

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009140

Luminaire Tested: S122DIP-B485D725UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009140
REPORT IS A COMBINATION OF REPORTS P984333 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D725UB35-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4923.0 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009140

CATALOG NUMBER: S122DIP-B485D725UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1009140

CATALOG NUMBER: S122DIP-B485D725UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50
1	97	93	89	86	88	85	82	79	71	68	66	57	56	54	45	44	43
2	88	81	76	71	81	75	70	65	62	59	56	51	48	46	40	38	37
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32
4	74	64	56	50	68	59	52	47	49	44	41	41	37	34	32	30	28
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	29	27	25
6	63	51	43	38	58	47	41	36	40	35	31	33	29	26	27	24	22
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20
8	54	42	35	30	50	39	32	28	33	28	24	28	24	21	23	20	18
9	50	39	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15383	15383	15383	15383
5°	15419	16401	15478	13049
10°	15240	17905	15336	10758
15°	14871	18885	15077	9062
20°	14638	17732	14638	7877
25°	14172	15233	14236	7044
30°	13404	11974	13659	6380
35°	12724	8280	12937	5837
40°	11943	6252	12079	5404
45°	10979	5138	11158	4937
50°	10147	4510	10163	4520
55°	9196	3842	9254	4066
60°	8181	3210	8296	3549
65°	7277	2610	7408	3031
70°	6370	2049	6535	2445
75°	5348	1487	5555	1772
80°	4176	942	4471	1051
85°	2740	475	2952	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15901 cd/sqm

TEST NUMBER: P1009140

CATALOG NUMBER: S122DIP-B485D725UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.6	1.9
10°-20°	269.4	5.5
20°-30°	391.0	7.9
30°-40°	412.2	8.4
40°-50°	364.7	7.4
50°-60°	291.2	5.9
60°-70°	197.8	4.0
70°-80°	101.2	2.1
80°-90°	26.5	0.5
90°-100°	155.4	3.2
100°-110°	547.3	11.1
110°-120°	574.8	11.7
120°-130°	472.9	9.6
130°-140°	379.9	7.7
140°-150°	287.0	5.8
150°-160°	201.7	4.1
160°-170°	118.8	2.4
170°-180°	38.6	0.8
0°-30°	752.9	15.3
0°-40°	1165.1	23.7
0°-60°	1821.1	37.0
0°-90°	2146.6	43.6
90°-120°	1277.5	26.0
90°-150°	2417.3	49.1
90°-180°	2776.0	56.4
0°-180°	4923.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	972	972	972	972	972	
5°	972	1085	976	864	972	92
15°	914	1334	926	640	914	258
25°	821	1111	825	514	821	375
35°	670	605	681	426	670	419
45°	503	364	511	350	503	390
55°	345	256	347	271	345	308
65°	205	158	208	183	205	203
75°	96	78	99	93	96	103
85°	19	20	21	15	19	23
90°	1	25	1	25	1	3
95°	27	87	27	87	27	28
105°	94	864	94	864	94	99
115°	165	1137	165	1137	165	163
125°	230	922	230	922	230	204
135°	270	764	270	764	270	208
145°	308	610	308	610	308	193
155°	350	513	350	513	350	161
165°	382	450	382	450	382	108
175°	398	406	398	406	398	38
180°	399	399	399	399	399	

TEST NUMBER: P1009140

CATALOG NUMBER: S122DIP-B485D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	977.0	979.2	983.0	983.7	991.2	997.2	1003.9	1003.9	1006.1	1005.4	999.4
5°	972.5	979.2	988.9	997.2	1010.6	1016.6	1025.5	1032.3	1038.2	1042.7	1042.0
7.5°	965.0	977.0	991.2	1006.9	1024.8	1035.3	1047.9	1059.9	1068.1	1075.6	1080.8
10°	952.3	972.5	991.9	1012.8	1036.0	1050.2	1065.1	1080.8	1093.5	1107.7	1121.1
12.5°	935.2	964.3	988.2	1015.8	1044.2	1059.9	1083.8	1095.8	1120.4	1156.3	1166.0
15°	913.5	953.1	975.5	1010.6	1047.9	1060.6	1093.5	1112.9	1163.7	1186.1	1213.0
17.5°	893.3	937.4	967.3	1007.6	1044.2	1068.9	1101.0	1140.6	1183.1	1215.3	1245.1
20°	876.9	919.5	955.3	1000.1	1046.5	1077.8	1111.4	1159.2	1205.6	1238.4	1261.6
22.5°	839.6	894.1	935.9	986.0	1042.0	1085.3	1117.4	1169.7	1219.7	1239.9	1260.1
25°	820.9	867.9	916.5	973.3	1039.0	1090.5	1118.2	1176.4	1220.5	1228.0	1232.4
27.5°	786.5	839.6	896.3	961.3	1038.2	1081.6	1116.7	1169.7	1204.8	1199.6	1186.1
30°	743.9	808.9	871.7	941.9	1027.8	1074.8	1107.7	1156.3	1174.2	1147.3	1123.4
32.5°	712.6	773.8	843.3	924.7	1015.8	1060.6	1092.8	1130.9	1134.6	1086.0	1045.7
35°	670.0	738.0	816.4	902.3	995.7	1036.0	1065.9	1089.0	1071.1	1003.1	955.3
37.5°	631.9	699.1	782.8	870.2	968.0	1007.6	1031.5	1035.3	991.2	931.4	861.2
40°	590.1	659.5	746.9	838.8	937.4	971.8	986.7	975.5	912.0	842.5	761.1
42.5°	548.2	617.0	711.1	805.2	898.6	927.7	933.7	903.0	825.4	743.9	649.8
45°	502.7	574.4	668.5	763.4	853.7	870.2	870.9	826.9	735.0	649.8	562.4
47.5°	465.3	531.8	625.2	720.0	796.2	807.4	803.0	752.2	652.1	556.5	480.3
50°	424.3	487.7	580.4	673.7	738.7	741.7	730.5	658.0	560.2	472.8	412.3
52.5°	380.2	444.4	529.6	619.2	677.5	673.0	651.3	573.6	481.8	409.3	363.0
55°	345.1	401.9	481.8	569.2	610.2	597.5	573.6	494.5	422.0	360.8	320.4
57.5°	306.2	356.3	434.7	510.9	534.8	522.9	499.0	425.0	357.8	311.5	284.6
60°	269.6	315.2	383.9	447.4	466.1	453.4	425.8	359.3	310.7	271.9	251.7
62.5°	236.0	275.6	333.1	391.4	398.9	386.2	362.3	308.5	266.7	236.0	221.1
65°	204.7	242.0	288.3	332.4	339.1	325.7	301.0	262.2	227.1	207.6	193.5
67.5°	174.0	203.9	245.0	277.1	280.8	268.1	248.0	216.6	194.9	174.0	163.6
70°	147.1	169.6	201.7	227.8	229.3	217.4	206.9	178.5	162.1	147.1	138.9
72.5°	121.0	136.7	161.3	180.8	181.5	174.0	164.3	146.4	132.2	121.8	113.5
75°	95.6	109.1	124.0	141.2	140.4	134.4	127.0	115.8	103.8	97.1	93.4
77.5°	73.2	81.4	93.4	104.6	104.6	101.6	97.1	88.9	81.4	74.7	71.0
80°	52.3	57.5	67.2	71.0	72.5	71.7	68.0	62.0	59.0	53.8	52.3
82.5°	33.6	37.3	41.8	45.6	47.8	46.3	45.6	42.6	38.1	36.6	35.1
85°	19.4	20.9	23.2	25.4	26.1	25.4	26.9	24.6	22.4	22.4	21.7
87.5°	8.2	9.0	10.5	10.5	11.2	11.2	10.5	11.2	11.2	10.5	9.7
90°	0.8	3.1	6.1	7.7	9.2	10.4	11.5	15.3	20.7	25.3	26.1
92.5°	11.5	16.1	22.2	26.1	32.2	36.4	40.6	61.3	90.5	116.5	118.1
95°	26.8	29.9	37.6	44.5	56.7	65.9	75.1	110.4	177.1	266.0	300.5
97.5°	39.9	44.5	52.9	62.9	76.7	87.1	97.4	142.6	235.4	378.7	489.9
100°	59.0	61.3	68.2	80.5	95.8	106.6	117.3	157.9	251.5	417.1	605.7
102.5°	76.7	78.2	85.1	97.4	113.5	124.2	134.9	171.7	252.2	402.5	609.5
105°	93.5	96.6	102.0	113.5	130.3	141.0	151.8	187.8	256.1	382.6	568.1
107.5°	111.9	114.2	119.6	130.3	147.2	158.0	168.7	203.9	264.5	371.8	529.8
110°	130.3	133.4	138.0	148.0	164.1	175.2	186.3	220.0	275.2	368.8	503.7

TEST NUMBER: P1009140

CATALOG NUMBER: S122DIP-B485D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	147.2	150.3	155.6	164.8	180.2	191.7	203.2	235.4	286.7	369.5	486.9
115°	164.8	168.7	173.3	182.5	197.8	208.2	218.5	251.5	298.2	372.6	475.4
117.5°	183.2	186.3	190.9	199.3	213.9	224.6	235.4	266.0	310.5	377.2	469.2
120°	200.1	203.2	207.8	214.7	230.0	240.8	251.5	281.4	322.8	381.8	463.9
122.5°	216.2	218.5	223.1	230.8	246.1	257.2	268.3	295.9	333.5	387.2	460.8
125°	230.0	232.3	236.9	246.1	261.4	272.2	282.9	310.5	345.0	392.5	457.0
127.5°	241.5	244.6	250.7	260.7	275.2	286.4	297.5	324.3	355.7	397.9	454.7
130°	251.5	254.5	262.2	272.9	288.3	299.0	309.7	336.6	365.7	404.0	453.1
132.5°	260.7	264.5	272.9	284.4	300.5	311.2	322.0	347.3	375.7	410.2	452.4
135°	269.9	272.9	282.1	293.6	311.3	322.0	332.7	357.3	384.1	414.8	451.6
137.5°	278.3	282.1	291.3	303.6	321.2	331.2	341.2	365.7	391.0	419.4	451.6
140°	288.3	291.3	300.5	312.8	329.7	339.6	349.6	372.6	396.4	422.5	450.8
142.5°	298.2	300.5	309.0	321.2	337.3	346.5	355.7	378.0	401.0	424.8	450.8
145°	308.2	311.3	318.9	330.4	345.8	354.2	362.6	383.3	404.8	426.3	449.3
147.5°	318.9	321.2	328.9	339.6	352.7	360.4	368.0	387.9	407.1	427.1	447.0
150°	329.7	332.0	338.1	348.1	359.6	366.5	373.4	391.0	408.6	426.3	444.7
152.5°	340.4	341.2	347.3	355.7	366.5	372.6	378.7	394.1	409.4	424.8	440.9
155°	350.4	351.1	355.7	364.2	372.6	378.4	384.1	397.1	410.2	423.2	436.3
157.5°	358.8	359.6	363.4	371.1	378.0	383.0	387.9	399.4	410.2	420.2	431.7
160°	367.2	368.0	371.1	377.2	383.3	387.6	391.8	401.0	410.2	417.9	427.1
162.5°	375.7	374.9	378.0	382.6	387.9	391.0	394.1	401.7	409.4	415.6	423.2
165°	381.8	381.0	382.6	387.2	391.0	393.3	395.6	402.5	407.9	412.5	417.9
167.5°	387.2	386.4	387.9	391.0	394.1	395.6	397.1	402.5	407.1	409.4	413.3
170°	392.5	391.0	391.8	394.1	395.6	396.8	397.9	401.7	405.6	407.1	409.4
172.5°	395.6	394.8	394.1	396.4	397.1	397.9	398.7	401.0	403.3	404.0	404.8
175°	397.9	397.1	396.4	397.9	397.9	398.3	398.7	400.2	401.7	401.0	401.7
177.5°	399.4	397.9	397.1	398.7	398.7	398.7	398.7	399.4	401.0	399.4	398.7
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P1009140

CATALOG NUMBER: S122DIP-B485D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	1009.9	1010.6	1012.1	1019.6	1023.3	1024.0	1021.1	1027.8	1030.0	1027.8	1026.3
5°	1057.7	1062.1	1071.1	1080.8	1080.1	1080.8	1085.3	1089.8	1091.3	1085.3	1087.5
7.5°	1099.5	1108.4	1118.2	1133.1	1133.1	1140.6	1143.6	1147.3	1156.3	1151.8	1150.3
10°	1147.3	1159.2	1177.2	1201.1	1201.8	1209.3	1216.8	1228.7	1232.4	1229.5	1230.9
12.5°	1207.0	1230.2	1231.7	1257.8	1269.8	1271.3	1283.2	1281.0	1288.5	1288.5	1301.2
15°	1233.2	1269.0	1289.2	1314.6	1322.1	1313.1	1322.8	1333.3	1334.0	1334.0	1333.3
17.5°	1280.2	1294.4	1314.6	1328.0	1331.0	1331.0	1331.8	1336.3	1333.3	1327.3	1331.8
20°	1290.0	1295.9	1303.4	1301.9	1303.4	1295.9	1288.5	1281.0	1281.7	1278.0	1289.2
22.5°	1272.0	1270.5	1253.4	1242.2	1242.2	1227.2	1213.0	1206.3	1199.6	1201.8	1205.6
25°	1227.2	1204.1	1183.1	1166.7	1163.0	1139.1	1119.7	1113.7	1102.5	1111.4	1112.9
27.5°	1155.5	1129.4	1095.8	1081.6	1062.1	1052.4	1039.0	1021.1	997.9	1011.3	1009.1
30°	1078.6	1039.7	1012.1	977.7	947.1	944.9	919.5	889.6	877.6	877.6	884.4
32.5°	992.7	941.1	900.8	852.3	822.4	809.7	779.1	749.2	755.9	733.5	741.7
35°	892.6	824.6	773.8	726.8	704.4	689.4	649.8	633.4	615.5	605.0	624.4
37.5°	797.0	718.6	653.6	602.0	593.8	566.9	540.0	529.6	519.1	523.6	522.9
40°	680.5	611.0	552.7	512.4	498.2	485.5	467.6	454.9	448.2	451.9	452.6
42.5°	575.1	516.9	473.6	445.2	433.2	424.3	415.3	404.8	402.6	402.6	405.6
45°	493.7	445.9	416.8	393.6	386.9	380.2	373.5	369.0	367.5	364.5	366.7
47.5°	428.7	390.6	372.7	355.5	348.1	346.6	340.6	338.4	335.4	334.6	335.4
50°	374.2	350.3	333.9	324.2	318.9	316.7	313.7	309.2	307.7	311.5	310.0
52.5°	336.1	313.7	304.7	295.0	292.1	289.1	284.6	285.3	284.6	283.1	283.1
55°	298.0	283.8	274.9	267.4	266.7	263.7	259.9	258.4	257.7	256.2	258.4
57.5°	267.4	256.2	248.0	241.3	238.3	238.3	234.5	231.5	231.5	230.8	231.5
60°	236.8	225.6	220.3	213.6	211.4	210.6	208.4	206.9	204.7	204.7	204.7
62.5°	208.4	199.4	193.5	187.5	188.2	184.5	181.5	180.0	180.0	180.8	180.8
65°	181.5	175.5	168.1	162.8	161.3	160.6	159.1	158.3	156.1	157.6	157.6
67.5°	156.9	148.6	144.2	141.9	139.7	138.9	137.4	135.9	135.2	134.4	135.9
70°	132.2	125.5	121.8	120.3	118.0	117.3	116.5	114.3	115.0	115.8	116.5
72.5°	109.8	103.8	103.1	98.6	98.6	98.6	95.6	97.1	96.4	94.9	96.4
75°	86.6	83.7	82.2	79.9	80.7	79.9	79.2	76.9	76.9	77.7	78.4
77.5°	68.7	65.7	65.0	62.7	61.2	62.7	61.2	60.5	60.5	61.2	61.2
80°	50.8	49.3	47.1	47.1	47.1	46.3	46.3	46.3	45.6	44.8	45.6
82.5°	33.6	33.6	32.9	32.1	32.9	31.4	32.1	32.1	32.1	32.1	32.1
85°	21.7	20.9	20.9	20.2	20.2	20.2	20.9	19.4	19.4	20.2	20.2
87.5°	9.7	9.7	9.7	10.5	9.7	9.7	9.7	10.5	9.7	9.7	9.7
90°	25.3	24.5	23.0	24.5	24.9	25.3	25.3	25.3	25.3	25.3	25.3
92.5°	98.9	77.4	65.9	57.5	54.4	51.4	50.6	47.5	48.3	46.8	48.3
95°	263.0	200.9	154.1	121.9	113.4	105.0	95.1	88.9	86.6	87.4	86.6
97.5°	493.8	410.9	328.1	250.7	227.7	204.7	174.8	159.5	151.0	146.4	151.0
100°	716.1	700.0	604.9	499.9	453.5	407.1	343.5	310.5	288.3	274.5	288.3
102.5°	798.9	889.4	886.3	816.5	766.7	716.9	646.3	584.2	555.1	535.2	555.1
105°	772.1	931.5	1018.2	1028.1	1015.4	1002.8	955.3	907.8	874.8	864.1	874.8
107.5°	715.3	886.3	1015.1	1090.2	1105.6	1120.9	1120.1	1113.2	1103.3	1085.6	1103.3
110°	662.4	824.2	961.4	1059.6	1091.0	1122.4	1155.4	1170.0	1176.9	1176.1	1176.9

TEST NUMBER: P1009140

CATALOG NUMBER: S122DIP-B485D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	625.6	767.5	897.8	1004.4	1041.6	1078.7	1127.8	1154.6	1169.2	1174.6	1169.2
115°	596.5	723.0	841.1	941.5	981.0	1020.5	1074.9	1110.2	1130.1	1137.0	1130.1
117.5°	576.6	686.2	792.0	885.5	923.1	960.7	1016.6	1054.2	1074.9	1080.3	1074.9
120°	561.2	660.1	755.2	836.5	871.4	906.2	959.9	995.9	1018.2	1025.8	1018.2
122.5°	548.2	639.4	724.5	800.4	831.1	861.8	908.5	943.8	963.0	969.1	963.0
125°	535.9	619.5	698.5	765.9	794.6	823.4	867.9	897.0	916.2	922.3	916.2
127.5°	524.4	599.6	672.4	736.8	763.6	790.5	829.6	857.2	874.0	878.6	874.0
130°	512.9	580.4	646.3	706.9	732.2	757.5	795.1	821.1	836.5	842.6	836.5
132.5°	503.7	562.0	621.8	676.2	699.6	723.0	759.8	785.9	799.7	805.0	799.7
135°	495.3	545.1	595.7	646.3	667.8	689.3	722.2	747.5	761.3	764.4	761.3
137.5°	489.2	531.3	575.0	616.4	635.6	654.8	686.2	708.4	720.7	725.3	720.7
140°	483.8	518.3	555.1	590.4	607.2	624.1	648.6	668.6	680.1	684.7	680.1
142.5°	478.4	507.6	537.5	566.6	580.0	593.4	616.4	634.1	644.0	644.0	644.0
145°	473.8	497.6	522.9	546.7	557.8	568.9	587.3	600.3	608.0	610.3	608.0
147.5°	469.2	489.9	510.6	529.8	538.2	546.7	562.8	573.5	578.9	580.4	578.9
150°	463.1	481.5	498.4	514.5	521.4	528.3	539.8	549.0	553.6	554.3	553.6
152.5°	457.7	473.1	488.4	501.4	507.2	512.9	521.4	529.0	532.1	532.1	532.1
155°	450.8	465.4	477.7	489.2	493.4	497.6	506.0	511.4	514.5	512.9	514.5
157.5°	444.7	456.2	466.9	476.9	480.4	483.8	489.9	494.5	496.1	496.1	496.1
160°	437.8	447.8	456.2	464.6	467.3	470.0	475.4	479.2	480.0	480.0	480.0
162.5°	431.7	439.3	446.2	453.1	455.0	457.0	462.3	464.6	465.4	464.6	465.4
165°	424.8	430.9	436.3	441.6	443.2	444.7	447.8	450.8	450.8	450.1	450.8
167.5°	417.9	422.5	427.1	430.9	432.4	434.0	435.5	437.0	437.0	436.3	437.0
170°	412.5	416.3	418.6	421.7	422.4	423.2	424.0	426.3	425.5	424.0	425.5
172.5°	407.1	409.4	410.9	413.3	413.6	414.0	414.8	415.6	414.8	414.0	414.8
175°	402.5	404.8	405.6	406.3	406.7	407.1	407.1	407.9	407.1	405.6	407.1
177.5°	399.4	401.0	401.0	401.7	401.7	401.7	401.7	401.7	401.0	399.4	401.0
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P1009140

CATALOG NUMBER: S122DIP-B485D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	1030.0	1024.8	1020.3	1021.1	1024.8	1021.8	1014.3	1004.6	1000.9	996.4	1000.9
5°	1092.0	1087.5	1078.6	1079.3	1077.1	1074.1	1062.1	1047.2	1047.2	1035.3	1033.8
7.5°	1153.3	1146.5	1140.6	1139.1	1130.9	1124.9	1114.4	1093.5	1085.3	1071.1	1062.9
10°	1222.0	1216.8	1210.0	1201.8	1197.3	1186.9	1169.7	1139.1	1124.1	1104.7	1090.5
12.5°	1291.4	1290.7	1275.8	1259.3	1258.6	1242.2	1230.2	1189.1	1169.0	1142.8	1109.2
15°	1335.5	1331.8	1323.6	1315.4	1317.6	1299.7	1272.8	1224.2	1210.8	1179.4	1143.6
17.5°	1334.8	1334.8	1332.5	1331.0	1328.8	1323.6	1308.6	1276.5	1254.8	1215.3	1181.6
20°	1292.2	1301.9	1304.1	1303.4	1310.9	1314.6	1313.9	1293.7	1276.5	1241.4	1207.0
22.5°	1207.0	1229.5	1239.2	1245.1	1260.8	1269.0	1288.5	1281.0	1276.5	1250.4	1221.2
25°	1127.9	1135.3	1164.5	1166.0	1187.6	1207.8	1227.2	1239.9	1256.3	1246.6	1222.0
27.5°	1025.5	1042.7	1063.6	1079.3	1083.8	1124.9	1157.0	1180.9	1218.2	1221.2	1213.0
30°	909.8	918.0	952.3	973.3	997.2	1027.0	1073.3	1114.4	1148.0	1178.7	1189.1
32.5°	768.6	802.2	822.4	847.8	868.7	921.7	978.5	1031.5	1070.4	1121.9	1144.3
35°	639.4	665.5	699.9	710.3	748.4	793.2	867.2	935.2	994.2	1046.5	1092.0
37.5°	532.6	553.5	590.1	606.5	628.9	686.4	748.4	832.8	903.8	968.0	1024.8
40°	459.4	475.0	502.7	507.9	526.6	578.9	628.9	708.1	802.2	888.9	950.8
42.5°	409.3	416.8	435.5	442.2	454.1	489.2	534.1	608.8	696.1	785.8	873.2
45°	373.5	378.7	389.9	395.9	410.8	426.5	463.1	522.9	591.6	682.0	776.1
47.5°	341.3	348.1	352.6	356.3	364.5	381.7	405.6	449.7	515.4	598.3	689.4
50°	314.5	316.7	324.9	325.7	330.9	342.1	364.5	391.4	443.7	510.9	599.0
52.5°	287.6	289.8	295.0	300.3	302.5	311.5	326.4	348.8	387.7	440.7	519.1
55°	260.7	263.7	268.9	272.6	274.9	282.3	291.3	313.0	343.6	380.9	445.2
57.5°	233.8	240.5	242.0	244.2	248.0	256.2	264.4	277.1	301.0	335.4	382.4
60°	208.4	210.6	215.9	218.1	221.8	226.3	236.8	246.5	263.7	290.6	333.1
62.5°	182.3	187.5	189.7	192.0	194.9	200.2	206.9	217.4	232.3	254.0	287.6
65°	159.8	160.6	165.1	168.1	171.0	174.8	181.5	191.2	200.2	220.3	245.0
67.5°	138.2	139.7	141.2	144.2	147.9	151.6	157.6	162.8	174.0	187.5	206.9
70°	117.3	117.3	121.0	123.2	122.5	127.0	131.5	137.4	145.7	158.3	174.0
72.5°	98.6	97.8	100.8	101.6	103.1	106.1	109.1	115.0	119.5	129.2	141.2
75°	78.4	79.9	81.4	81.4	83.7	85.9	88.9	91.9	97.1	103.1	112.0
77.5°	62.0	62.0	63.5	64.2	66.5	65.7	68.7	71.7	75.4	80.7	87.4
80°	45.6	47.1	47.1	47.1	47.8	48.6	51.5	53.8	56.0	59.8	62.7
82.5°	32.1	32.1	33.6	33.6	33.6	35.1	35.1	35.9	37.3	39.6	41.8
85°	20.2	20.2	20.2	20.9	20.2	20.9	22.4	21.7	22.4	23.9	23.9
87.5°	9.7	9.7	9.7	9.7	9.7	10.5	9.7	10.5	11.2	11.2	11.2
90°	25.3	25.3	25.3	24.9	24.5	23.0	24.5	25.3	26.1	25.3	20.7
92.5°	47.5	50.6	51.4	54.4	57.5	65.9	77.4	98.9	118.1	116.5	90.5
95°	88.9	95.1	105.0	113.4	121.9	154.1	200.9	263.0	300.5	266.0	177.1
97.5°	159.5	174.8	204.7	227.7	250.7	328.1	410.9	493.8	489.9	378.7	235.4
100°	310.5	343.5	407.1	453.5	499.9	604.9	700.0	716.1	605.7	417.1	251.5
102.5°	584.2	646.3	716.9	766.7	816.5	886.3	889.4	798.9	609.5	402.5	252.2
105°	907.8	955.3	1002.8	1015.4	1028.1	1018.2	931.5	772.1	568.1	382.6	256.1
107.5°	1113.2	1120.1	1120.9	1105.6	1090.2	1015.1	886.3	715.3	529.8	371.8	264.5
110°	1170.0	1155.4	1122.4	1091.0	1059.6	961.4	824.2	662.4	503.7	368.8	275.2

TEST NUMBER: P1009140

CATALOG NUMBER: S122DIP-B485D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1154.6	1127.8	1078.7	1041.6	1004.4	897.8	767.5	625.6	486.9	369.5	286.7
115°	1110.2	1074.9	1020.5	981.0	941.5	841.1	723.0	596.5	475.4	372.6	298.2
117.5°	1054.2	1016.6	960.7	923.1	885.5	792.0	686.2	576.6	469.2	377.2	310.5
120°	995.9	959.9	906.2	871.4	836.5	755.2	660.1	561.2	463.9	381.8	322.8
122.5°	943.8	908.5	861.8	831.1	800.4	724.5	639.4	548.2	460.8	387.2	333.5
125°	897.0	867.9	823.4	794.6	765.9	698.5	619.5	535.9	457.0	392.5	345.0
127.5°	857.2	829.6	790.5	763.6	736.8	672.4	599.6	524.4	454.7	397.9	355.7
130°	821.1	795.1	757.5	732.2	706.9	646.3	580.4	512.9	453.1	404.0	365.7
132.5°	785.9	759.8	723.0	699.6	676.2	621.8	562.0	503.7	452.4	410.2	375.7
135°	747.5	722.2	689.3	667.8	646.3	595.7	545.1	495.3	451.6	414.8	384.1
137.5°	708.4	686.2	654.8	635.6	616.4	575.0	531.3	489.2	451.6	419.4	391.0
140°	668.6	648.6	624.1	607.2	590.4	555.1	518.3	483.8	450.8	422.5	396.4
142.5°	634.1	616.4	593.4	580.0	566.6	537.5	507.6	478.4	450.8	424.8	401.0
145°	600.3	587.3	568.9	557.8	546.7	522.9	497.6	473.8	449.3	426.3	404.8
147.5°	573.5	562.8	546.7	538.2	529.8	510.6	489.9	469.2	447.0	427.1	407.1
150°	549.0	539.8	528.3	521.4	514.5	498.4	481.5	463.1	444.7	426.3	408.6
152.5°	529.0	521.4	512.9	507.2	501.4	488.4	473.1	457.7	440.9	424.8	409.4
155°	511.4	506.0	497.6	493.4	489.2	477.7	465.4	450.8	436.3	423.2	410.2
157.5°	494.5	489.9	483.8	480.4	476.9	466.9	456.2	444.7	431.7	420.2	410.2
160°	479.2	475.4	470.0	467.3	464.6	456.2	447.8	437.8	427.1	417.9	410.2
162.5°	464.6	462.3	457.0	455.0	453.1	446.2	439.3	431.7	423.2	415.6	409.4
165°	450.8	447.8	444.7	443.2	441.6	436.3	430.9	424.8	417.9	412.5	407.9
167.5°	437.0	435.5	434.0	432.4	430.9	427.1	422.5	417.9	413.3	409.4	407.1
170°	426.3	424.0	423.2	422.4	421.7	418.6	416.3	412.5	409.4	407.1	405.6
172.5°	415.6	414.8	414.0	413.6	413.3	410.9	409.4	407.1	404.8	404.0	403.3
175°	407.9	407.1	407.1	406.7	406.3	405.6	404.8	402.5	401.7	401.0	401.7
177.5°	401.7	401.7	401.7	401.7	401.7	401.0	401.0	399.4	398.7	399.4	401.0
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P1009140

CATALOG NUMBER: S122DIP-B485D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	997.2	993.4	991.2	992.7	988.2	977.0	977.0	980.7	976.2	971.8	965.0
5°	1024.8	1017.3	1012.8	1012.1	1001.6	983.7	980.0	976.2	966.5	956.1	944.9
7.5°	1051.7	1038.2	1030.8	1025.5	1010.6	987.4	977.7	969.5	953.8	938.1	924.0
10°	1074.1	1054.7	1045.7	1037.5	1018.1	988.9	973.3	958.3	938.1	918.0	900.1
12.5°	1092.0	1069.6	1058.4	1046.5	1022.6	984.5	965.0	941.1	921.0	894.1	876.2
15°	1121.9	1075.6	1065.1	1053.9	1029.3	977.0	953.1	926.2	898.6	862.7	843.3
17.5°	1145.8	1083.8	1083.1	1059.2	1027.0	974.0	937.4	902.3	872.4	836.6	805.9
20°	1160.0	1096.5	1084.5	1059.9	1019.6	953.8	915.7	876.9	844.8	801.5	770.8
22.5°	1171.9	1114.4	1083.1	1053.2	1003.9	947.1	891.1	854.5	810.4	763.4	734.2
25°	1176.4	1118.2	1085.3	1050.9	992.7	927.7	864.2	824.6	775.3	732.7	693.2
27.5°	1177.2	1117.4	1077.1	1041.2	977.0	902.3	837.3	795.5	741.0	691.7	652.1
30°	1169.7	1109.2	1072.6	1033.8	962.1	879.1	804.4	758.1	699.9	650.6	609.5
32.5°	1147.3	1092.8	1062.9	1020.3	942.6	847.0	773.1	721.5	660.3	611.7	572.2
35°	1109.9	1072.6	1039.7	1000.1	917.2	817.1	741.7	681.2	619.2	572.9	535.6
37.5°	1063.6	1043.5	1012.8	974.0	888.1	790.3	706.6	639.4	577.4	532.6	496.0
40°	1000.9	1006.1	976.2	941.1	853.7	753.7	661.0	596.8	538.5	496.7	460.9
42.5°	932.9	954.6	937.4	903.8	815.7	713.3	627.4	556.5	499.7	456.4	426.5
45°	859.7	897.1	886.6	862.0	776.1	670.7	579.6	510.9	460.9	419.0	392.9
47.5°	779.8	832.8	832.8	814.9	732.0	628.2	538.5	468.3	419.0	389.2	363.8
50°	698.4	758.1	767.8	755.9	682.7	579.6	488.5	425.0	382.4	353.3	334.6
52.5°	613.2	682.7	700.6	694.6	630.4	533.3	447.4	385.4	346.6	321.2	304.7
55°	531.8	612.5	631.9	634.1	574.4	482.5	401.9	347.3	310.0	292.8	278.6
57.5°	454.9	532.6	554.2	558.0	517.6	436.2	359.3	311.5	277.9	263.7	252.5
60°	389.2	454.1	482.5	490.7	455.6	382.4	319.7	273.4	248.0	234.5	224.1
62.5°	335.4	387.7	417.5	419.8	404.1	335.4	278.6	239.8	218.1	206.2	200.9
65°	283.1	330.1	348.1	357.0	344.3	290.6	240.5	208.4	191.2	180.8	175.5
67.5°	241.3	271.1	286.1	298.0	285.3	245.0	204.7	178.5	165.8	155.4	152.4
70°	197.9	222.6	233.8	245.7	234.5	203.9	174.8	150.9	139.7	131.5	127.7
72.5°	158.3	177.8	188.2	195.7	189.0	163.6	139.7	123.2	115.0	109.1	106.8
75°	125.5	138.9	144.9	150.1	147.1	127.7	112.8	99.3	91.9	86.6	85.2
77.5°	95.6	105.3	112.0	113.5	109.8	97.1	84.4	76.2	70.2	67.2	65.7
80°	68.0	73.9	77.7	79.9	76.2	71.0	62.0	56.0	50.8	47.1	46.3
82.5°	45.6	48.6	51.5	50.8	49.3	44.8	39.6	36.6	34.4	31.4	31.4
85°	26.1	26.9	28.4	29.1	28.4	25.4	22.4	20.9	19.4	17.2	17.2
87.5°	11.2	12.0	12.0	12.7	11.2	11.2	9.7	8.2	8.2	7.5	6.7
90°	15.3	11.5	10.4	9.2	7.7	6.1	3.1	0.8	3.1	6.1	7.7
92.5°	61.3	40.6	36.4	32.2	26.1	22.2	16.1	11.5	16.1	22.2	26.1
95°	110.4	75.1	65.9	56.7	44.5	37.6	29.9	26.8	29.9	37.6	44.5
97.5°	142.6	97.4	87.1	76.7	62.9	52.9	44.5	39.9	44.5	52.9	62.9
100°	157.9	117.3	106.6	95.8	80.5	68.2	61.3	59.0	61.3	68.2	80.5
102.5°	171.7	134.9	124.2	113.5	97.4	85.1	78.2	76.7	78.2	85.1	97.4
105°	187.8	151.8	141.0	130.3	113.5	102.0	96.6	93.5	96.6	102.0	113.5
107.5°	203.9	168.7	158.0	147.2	130.3	119.6	114.2	111.9	114.2	119.6	130.3
110°	220.0	186.3	175.2	164.1	148.0	138.0	133.4	130.3	133.4	138.0	148.0

TEST NUMBER: P1009140

CATALOG NUMBER: S122DIP-B485D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	235.4	203.2	191.7	180.2	164.8	155.6	150.3	147.2	150.3	155.6	164.8
115°	251.5	218.5	208.2	197.8	182.5	173.3	168.7	164.8	168.7	173.3	182.5
117.5°	266.0	235.4	224.6	213.9	199.3	190.9	186.3	183.2	186.3	190.9	199.3
120°	281.4	251.5	240.8	230.0	214.7	207.8	203.2	200.1	203.2	207.8	214.7
122.5°	295.9	268.3	257.2	246.1	230.8	223.1	218.5	216.2	218.5	223.1	230.8
125°	310.5	282.9	272.2	261.4	246.1	236.9	232.3	230.0	232.3	236.9	246.1
127.5°	324.3	297.5	286.4	275.2	260.7	250.7	244.6	241.5	244.6	250.7	260.7
130°	336.6	309.7	299.0	288.3	272.9	262.2	254.5	251.5	254.5	262.2	272.9
132.5°	347.3	322.0	311.2	300.5	284.4	272.9	264.5	260.7	264.5	272.9	284.4
135°	357.3	332.7	322.0	311.3	293.6	282.1	272.9	269.9	272.9	282.1	293.6
137.5°	365.7	341.2	331.2	321.2	303.6	291.3	282.1	278.3	282.1	291.3	303.6
140°	372.6	349.6	339.6	329.7	312.8	300.5	291.3	288.3	291.3	300.5	312.8
142.5°	378.0	355.7	346.5	337.3	321.2	309.0	300.5	298.2	300.5	309.0	321.2
145°	383.3	362.6	354.2	345.8	330.4	318.9	311.3	308.2	311.3	318.9	330.4
147.5°	387.9	368.0	360.4	352.7	339.6	328.9	321.2	318.9	321.2	328.9	339.6
150°	391.0	373.4	366.5	359.6	348.1	338.1	332.0	329.7	332.0	338.1	348.1
152.5°	394.1	378.7	372.6	366.5	355.7	347.3	341.2	340.4	341.2	347.3	355.7
155°	397.1	384.1	378.4	372.6	364.2	355.7	351.1	350.4	351.1	355.7	364.2
157.5°	399.4	387.9	383.0	378.0	371.1	363.4	359.6	358.8	359.6	363.4	371.1
160°	401.0	391.8	387.6	383.3	377.2	371.1	368.0	367.2	368.0	371.1	377.2
162.5°	401.7	394.1	391.0	387.9	382.6	378.0	374.9	375.7	374.9	378.0	382.6
165°	402.5	395.6	393.3	391.0	387.2	382.6	381.0	381.8	381.0	382.6	387.2
167.5°	402.5	397.1	395.6	394.1	391.0	387.9	386.4	387.2	386.4	387.9	391.0
170°	401.7	397.9	396.8	395.6	394.1	391.8	391.0	392.5	391.0	391.8	394.1
172.5°	401.0	398.7	397.9	397.1	396.4	394.1	394.8	395.6	394.8	394.1	396.4
175°	400.2	398.7	398.3	397.9	397.9	396.4	397.1	397.9	397.1	396.4	397.9
177.5°	399.4	398.7	398.7	398.7	398.7	397.1	397.9	399.4	397.9	397.1	398.7
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P1009140

CATALOG NUMBER: S122DIP-B485D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	961.3	965.0	964.3	956.8	948.6	941.9	929.2	930.7	926.2	926.9	931.4
5°	937.4	937.4	934.4	924.0	910.5	903.0	888.9	885.1	876.2	875.4	874.7
7.5°	912.0	908.3	904.5	889.6	873.2	861.2	841.8	837.3	828.3	822.4	819.4
10°	882.1	876.9	869.4	852.3	832.1	817.1	797.0	791.0	773.8	766.4	761.9
12.5°	849.3	846.3	834.3	820.1	787.3	770.8	741.7	747.7	730.5	715.6	713.3
15°	816.4	805.2	798.5	775.3	735.7	728.3	705.1	693.2	677.5	665.5	665.5
17.5°	784.3	767.1	752.2	727.5	698.4	677.5	660.3	654.3	634.9	622.9	620.7
20°	741.7	722.3	718.6	683.4	663.3	640.1	623.7	608.8	594.6	589.3	585.6
22.5°	701.4	679.0	673.0	643.1	622.9	599.8	583.4	572.9	562.4	558.7	552.0
25°	658.0	644.6	635.6	603.5	581.1	559.5	548.2	540.8	531.1	530.3	525.8
27.5°	616.2	603.5	594.6	563.9	547.5	527.3	518.4	510.2	504.9	502.7	500.4
30°	580.4	566.2	555.7	533.3	513.1	496.7	489.2	484.0	481.0	477.3	476.5
32.5°	540.8	532.6	518.4	501.2	485.5	469.8	465.3	461.6	457.1	455.6	454.9
35°	507.2	496.0	487.0	467.6	460.9	447.4	442.2	439.2	433.2	431.7	430.2
37.5°	474.3	463.8	454.1	442.2	429.5	422.0	419.0	414.5	411.6	412.3	410.8
40°	441.4	433.2	425.8	413.1	405.6	401.9	395.9	391.4	389.9	390.6	389.9
42.5°	409.3	401.9	397.4	387.7	380.2	376.5	372.7	368.2	370.5	370.5	372.7
45°	380.2	373.5	370.5	363.0	358.5	352.6	348.8	348.1	351.1	350.3	350.3
47.5°	350.3	348.1	344.3	337.6	331.6	327.9	327.2	327.2	330.1	331.6	330.9
50°	327.2	322.7	318.2	313.0	308.5	307.0	304.7	306.2	309.2	309.2	310.7
52.5°	298.0	295.0	293.5	289.1	286.1	286.1	286.1	286.8	289.1	291.3	290.6
55°	272.6	270.4	268.9	266.7	262.9	263.7	262.9	264.4	266.7	268.9	270.4
57.5°	245.7	245.0	243.5	239.8	239.8	239.0	241.3	242.0	245.7	247.2	249.5
60°	221.8	219.6	219.6	216.6	216.6	216.6	218.9	221.1	224.1	224.8	226.3
62.5°	196.4	196.4	195.7	193.5	193.5	195.7	196.4	199.4	200.9	200.9	203.2
65°	172.5	171.8	171.0	171.8	172.5	172.5	174.8	176.3	177.8	178.5	179.3
67.5°	148.6	147.9	149.4	148.6	150.1	153.1	152.4	154.6	156.9	156.9	157.6
70°	126.2	127.7	127.0	128.5	127.7	129.2	131.5	132.2	132.2	133.0	135.2
72.5°	105.3	105.3	105.3	104.6	105.3	106.8	108.3	109.1	110.5	111.3	113.5
75°	85.2	85.2	83.7	85.2	85.2	86.6	88.1	88.1	88.1	89.6	91.9
77.5°	64.2	65.0	64.2	65.7	65.7	66.5	68.0	67.2	68.7	69.5	70.2
80°	47.1	46.3	46.3	46.3	47.1	47.1	48.6	49.3	49.3	51.5	50.0
82.5°	29.9	30.6	29.9	30.6	30.6	31.4	30.6	31.4	32.1	33.6	32.9
85°	17.2	16.4	16.4	17.2	16.4	16.4	17.2	16.4	17.2	16.4	17.2
87.5°	6.7	6.0	6.0	6.0	6.0	5.2	5.2	4.5	4.5	4.5	3.7
90°	9.2	10.4	11.5	15.3	20.7	25.3	26.1	25.3	24.5	23.0	24.5
92.5°	32.2	36.4	40.6	61.3	90.5	116.5	118.1	98.9	77.4	65.9	57.5
95°	56.7	65.9	75.1	110.4	177.1	266.0	300.5	263.0	200.9	154.1	121.9
97.5°	76.7	87.1	97.4	142.6	235.4	378.7	489.9	493.8	410.9	328.1	250.7
100°	95.8	106.6	117.3	157.9	251.5	417.1	605.7	716.1	700.0	604.9	499.9
102.5°	113.5	124.2	134.9	171.7	252.2	402.5	609.5	798.9	889.4	886.3	816.5
105°	130.3	141.0	151.8	187.8	256.1	382.6	568.1	772.1	931.5	1018.2	1028.1
107.5°	147.2	158.0	168.7	203.9	264.5	371.8	529.8	715.3	886.3	1015.1	1090.2
110°	164.1	175.2	186.3	220.0	275.2	368.8	503.7	662.4	824.2	961.4	1059.6

TEST NUMBER: P1009140

CATALOG NUMBER: S122DIP-B485D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	180.2	191.7	203.2	235.4	286.7	369.5	486.9	625.6	767.5	897.8	1004.4
115°	197.8	208.2	218.5	251.5	298.2	372.6	475.4	596.5	723.0	841.1	941.5
117.5°	213.9	224.6	235.4	266.0	310.5	377.2	469.2	576.6	686.2	792.0	885.5
120°	230.0	240.8	251.5	281.4	322.8	381.8	463.9	561.2	660.1	755.2	836.5
122.5°	246.1	257.2	268.3	295.9	333.5	387.2	460.8	548.2	639.4	724.5	800.4
125°	261.4	272.2	282.9	310.5	345.0	392.5	457.0	535.9	619.5	698.5	765.9
127.5°	275.2	286.4	297.5	324.3	355.7	397.9	454.7	524.4	599.6	672.4	736.8
130°	288.3	299.0	309.7	336.6	365.7	404.0	453.1	512.9	580.4	646.3	706.9
132.5°	300.5	311.2	322.0	347.3	375.7	410.2	452.4	503.7	562.0	621.8	676.2
135°	311.3	322.0	332.7	357.3	384.1	414.8	451.6	495.3	545.1	595.7	646.3
137.5°	321.2	331.2	341.2	365.7	391.0	419.4	451.6	489.2	531.3	575.0	616.4
140°	329.7	339.6	349.6	372.6	396.4	422.5	450.8	483.8	518.3	555.1	590.4
142.5°	337.3	346.5	355.7	378.0	401.0	424.8	450.8	478.4	507.6	537.5	566.6
145°	345.8	354.2	362.6	383.3	404.8	426.3	449.3	473.8	497.6	522.9	546.7
147.5°	352.7	360.4	368.0	387.9	407.1	427.1	447.0	469.2	489.9	510.6	529.8
150°	359.6	366.5	373.4	391.0	408.6	426.3	444.7	463.1	481.5	498.4	514.5
152.5°	366.5	372.6	378.7	394.1	409.4	424.8	440.9	457.7	473.1	488.4	501.4
155°	372.6	378.4	384.1	397.1	410.2	423.2	436.3	450.8	465.4	477.7	489.2
157.5°	378.0	383.0	387.9	399.4	410.2	420.2	431.7	444.7	456.2	466.9	476.9
160°	383.3	387.6	391.8	401.0	410.2	417.9	427.1	437.8	447.8	456.2	464.6
162.5°	387.9	391.0	394.1	401.7	409.4	415.6	423.2	431.7	439.3	446.2	453.1
165°	391.0	393.3	395.6	402.5	407.9	412.5	417.9	424.8	430.9	436.3	441.6
167.5°	394.1	395.6	397.1	402.5	407.1	409.4	413.3	417.9	422.5	427.1	430.9
170°	395.6	396.8	397.9	401.7	405.6	407.1	409.4	412.5	416.3	418.6	421.7
172.5°	397.1	397.9	398.7	401.0	403.3	404.0	404.8	407.1	409.4	410.9	413.3
175°	397.9	398.3	398.7	400.2	401.7	401.0	401.7	402.5	404.8	405.6	406.3
177.5°	398.7	398.7	398.7	399.4	401.0	399.4	398.7	399.4	401.0	401.0	401.7
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P1009140

CATALOG NUMBER: S122DIP-B485D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	926.2	928.4	923.2	921.7	923.2	918.0	919.5	921.0	921.0	923.2	924.7
5°	872.4	869.4	864.2	862.7	861.2	863.5	862.0	864.2	864.9	870.2	870.9
7.5°	819.4	814.9	810.4	805.9	804.4	800.7	804.4	804.4	809.7	808.2	811.9
10°	756.6	755.9	749.9	747.7	744.7	738.7	746.9	744.7	748.4	755.1	756.6
12.5°	710.3	702.1	705.9	695.4	699.1	693.2	693.9	693.9	699.9	700.6	699.1
15°	666.3	659.5	649.8	645.4	643.1	640.1	649.8	650.6	646.1	656.6	652.8
17.5°	621.4	621.4	612.5	610.2	604.3	607.3	605.8	606.5	605.0	612.5	616.2
20°	582.6	578.9	575.9	576.6	569.2	567.7	566.2	567.7	572.9	578.1	579.6
22.5°	551.2	549.0	541.5	543.0	537.0	539.3	537.8	541.5	542.3	542.3	547.5
25°	521.4	518.4	519.1	516.1	513.9	513.9	511.6	513.9	516.9	518.4	519.1
27.5°	499.0	496.7	493.0	490.7	492.2	488.5	491.5	493.7	493.7	492.2	493.7
30°	472.1	473.6	473.6	466.1	469.1	467.6	469.8	471.3	471.3	472.1	470.6
32.5°	454.1	449.7	448.9	448.2	448.2	445.2	445.2	447.4	448.2	448.9	451.1
35°	430.2	430.2	426.5	428.7	425.8	426.5	425.8	426.5	428.0	425.8	428.0
37.5°	408.6	409.3	407.8	409.3	410.1	408.6	407.1	410.1	408.6	408.6	407.1
40°	389.9	389.2	389.9	389.9	389.9	390.6	389.2	389.2	389.2	387.7	386.2
42.5°	374.2	369.7	371.2	372.0	369.7	369.7	370.5	369.7	372.0	367.5	367.5
45°	351.8	350.3	351.1	351.1	352.6	350.3	351.8	352.6	350.3	349.6	348.1
47.5°	331.6	333.1	331.6	333.1	333.1	334.6	331.6	332.4	333.1	330.1	327.9
50°	311.5	311.5	313.7	313.0	313.7	312.2	312.2	311.5	312.2	310.7	308.5
52.5°	292.8	290.6	294.3	293.5	292.8	292.1	291.3	292.1	290.6	289.1	289.1
55°	269.6	269.6	271.9	272.6	272.6	271.1	269.6	270.4	269.6	268.9	268.1
57.5°	251.0	248.0	249.5	250.2	250.2	248.0	249.5	248.0	248.0	248.7	246.5
60°	227.1	227.1	225.6	227.8	227.8	226.3	226.3	227.1	225.6	224.8	224.1
62.5°	201.7	202.4	204.7	205.4	206.2	204.7	203.2	203.9	203.9	201.7	202.4
65°	180.0	181.5	184.5	183.7	182.3	183.0	181.5	182.3	180.0	180.8	178.5
67.5°	159.1	158.3	159.1	159.1	160.6	159.8	158.3	158.3	157.6	159.8	157.6
70°	136.7	136.7	136.7	136.7	137.4	138.2	136.7	135.2	135.9	134.4	133.7
72.5°	113.5	114.3	113.5	115.0	112.8	114.3	114.3	113.5	112.8	112.8	112.8
75°	91.9	93.4	91.1	91.9	91.1	92.6	91.9	91.9	90.4	89.6	90.4
77.5°	70.2	71.0	69.5	70.2	69.5	70.2	70.2	69.5	69.5	69.5	69.5
80°	50.0	50.8	50.0	49.3	48.6	50.0	48.6	49.3	50.0	49.3	50.8
82.5°	32.1	32.1	31.4	32.1	30.6	30.6	31.4	31.4	30.6	32.1	30.6
85°	15.7	15.7	17.2	15.7	14.9	14.9	14.9	15.7	14.9	16.4	15.7
87.5°	3.7	3.0	3.7	3.7	3.0	3.0	3.7	3.0	3.7	4.5	3.0
90°	24.9	25.3	25.3	25.3	25.3	25.3	25.3	25.3	25.3	25.3	24.9
92.5°	54.4	51.4	50.6	47.5	48.3	46.8	48.3	47.5	50.6	51.4	54.4
95°	113.4	105.0	95.1	88.9	86.6	87.4	86.6	88.9	95.1	105.0	113.4
97.5°	227.7	204.7	174.8	159.5	151.0	146.4	151.0	159.5	174.8	204.7	227.7
100°	453.5	407.1	343.5	310.5	288.3	274.5	288.3	310.5	343.5	407.1	453.5
102.5°	766.7	716.9	646.3	584.2	555.1	535.2	555.1	584.2	646.3	716.9	766.7
105°	1015.4	1002.8	955.3	907.8	874.8	864.1	874.8	907.8	955.3	1002.8	1015.4
107.5°	1105.6	1120.9	1120.1	1113.2	1103.3	1085.6	1103.3	1113.2	1120.1	1120.9	1105.6
110°	1091.0	1122.4	1155.4	1170.0	1176.9	1176.1	1176.9	1170.0	1155.4	1122.4	1091.0

TEST NUMBER: P1009140

CATALOG NUMBER: S122DIP-B485D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1041.6	1078.7	1127.8	1154.6	1169.2	1174.6	1169.2	1154.6	1127.8	1078.7	1041.6
115°	981.0	1020.5	1074.9	1110.2	1130.1	1137.0	1130.1	1110.2	1074.9	1020.5	981.0
117.5°	923.1	960.7	1016.6	1054.2	1074.9	1080.3	1074.9	1054.2	1016.6	960.7	923.1
120°	871.4	906.2	959.9	995.9	1018.2	1025.8	1018.2	995.9	959.9	906.2	871.4
122.5°	831.1	861.8	908.5	943.8	963.0	969.1	963.0	943.8	908.5	861.8	831.1
125°	794.6	823.4	867.9	897.0	916.2	922.3	916.2	897.0	867.9	823.4	794.6
127.5°	763.6	790.5	829.6	857.2	874.0	878.6	874.0	857.2	829.6	790.5	763.6
130°	732.2	757.5	795.1	821.1	836.5	842.6	836.5	821.1	795.1	757.5	732.2
132.5°	699.6	723.0	759.8	785.9	799.7	805.0	799.7	785.9	759.8	723.0	699.6
135°	667.8	689.3	722.2	747.5	761.3	764.4	761.3	747.5	722.2	689.3	667.8
137.5°	635.6	654.8	686.2	708.4	720.7	725.3	720.7	708.4	686.2	654.8	635.6
140°	607.2	624.1	648.6	668.6	680.1	684.7	680.1	668.6	648.6	624.1	607.2
142.5°	580.0	593.4	616.4	634.1	644.0	644.0	644.0	634.1	616.4	593.4	580.0
145°	557.8	568.9	587.3	600.3	608.0	610.3	608.0	600.3	587.3	568.9	557.8
147.5°	538.2	546.7	562.8	573.5	578.9	580.4	578.9	573.5	562.8	546.7	538.2
150°	521.4	528.3	539.8	549.0	553.6	554.3	553.6	549.0	539.8	528.3	521.4
152.5°	507.2	512.9	521.4	529.0	532.1	532.1	532.1	529.0	521.4	512.9	507.2
155°	493.4	497.6	506.0	511.4	514.5	512.9	514.5	511.4	506.0	497.6	493.4
157.5°	480.4	483.8	489.9	494.5	496.1	496.1	496.1	494.5	489.9	483.8	480.4
160°	467.3	470.0	475.4	479.2	480.0	480.0	480.0	479.2	475.4	470.0	467.3
162.5°	455.0	457.0	462.3	464.6	465.4	464.6	465.4	464.6	462.3	457.0	455.0
165°	443.2	444.7	447.8	450.8	450.8	450.1	450.8	450.8	447.8	444.7	443.2
167.5°	432.4	434.0	435.5	437.0	437.0	436.3	437.0	437.0	435.5	434.0	432.4
170°	422.4	423.2	424.0	426.3	425.5	424.0	425.5	426.3	424.0	423.2	422.4
172.5°	413.6	414.0	414.8	415.6	414.8	414.0	414.8	415.6	414.8	414.0	413.6
175°	406.7	407.1	407.1	407.9	407.1	405.6	407.1	407.9	407.1	407.1	406.7
177.5°	401.7	401.7	401.7	401.7	401.0	399.4	401.0	401.7	401.7	401.7	401.7
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P1009140

CATALOG NUMBER: S122DIP-B485D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	922.5	928.4	926.2	918.0	927.7	927.7	934.4	934.4	942.6	945.6	950.1
5°	870.2	874.7	878.4	874.7	881.4	891.8	897.8	903.0	914.2	918.7	925.5
7.5°	814.2	822.4	826.1	826.1	837.3	849.3	861.2	868.7	884.4	890.3	897.1
10°	759.6	769.3	776.8	776.1	794.7	802.2	817.1	834.3	850.0	859.0	868.7
12.5°	702.1	707.3	717.8	732.7	737.2	750.7	767.8	789.5	817.9	826.1	840.3
15°	654.3	668.5	676.7	683.4	693.9	706.6	725.3	746.2	774.6	792.5	807.4
17.5°	614.0	632.7	637.9	636.4	649.8	669.3	690.9	706.6	732.0	753.7	767.8
20°	581.1	588.6	597.5	601.3	611.7	632.7	653.6	671.5	692.4	709.6	726.0
22.5°	548.2	554.2	561.7	568.4	576.6	588.6	608.8	631.2	651.3	667.8	686.4
25°	521.4	525.1	531.8	537.0	546.0	554.2	568.4	593.1	617.0	626.7	643.1
27.5°	495.2	498.2	502.7	508.7	513.1	521.4	534.1	554.2	578.9	588.6	611.0
30°	472.1	474.3	478.8	481.8	484.0	493.7	503.4	519.1	537.8	551.2	567.7
32.5°	450.4	452.6	457.1	457.9	460.9	466.1	475.0	489.2	505.7	516.9	531.1
35°	426.5	428.0	432.5	434.0	436.2	440.7	447.4	457.9	472.8	481.0	493.7
37.5°	407.8	407.1	410.1	412.3	415.3	417.5	419.8	430.2	441.4	448.9	458.6
40°	387.7	386.2	386.9	389.9	391.4	394.4	394.4	404.8	412.3	418.3	425.8
42.5°	367.5	366.7	365.3	366.7	368.2	369.0	369.7	377.2	384.7	389.9	398.1
45°	347.3	346.6	345.1	345.8	345.8	347.3	349.6	352.6	357.8	362.3	366.7
47.5°	328.7	327.2	324.9	324.2	325.7	325.7	325.7	328.7	333.9	335.4	339.9
50°	309.2	307.0	304.0	302.5	302.5	301.8	303.3	304.0	308.5	310.0	313.7
52.5°	288.3	286.8	283.8	280.8	281.6	280.1	280.8	281.6	283.1	285.3	287.6
55°	267.4	264.4	262.2	261.4	259.2	259.2	256.9	259.9	259.2	259.9	262.9
57.5°	247.2	244.2	240.5	239.0	236.8	236.0	234.5	233.8	234.5	236.8	239.0
60°	223.3	221.8	219.6	217.4	215.9	213.6	212.1	212.1	211.4	211.4	212.1
62.5°	200.2	199.4	196.4	195.7	194.2	192.7	190.5	189.0	189.0	190.5	191.2
65°	177.8	177.0	174.8	174.0	170.3	168.8	168.1	167.3	165.8	165.8	165.8
67.5°	156.9	154.6	154.6	150.9	147.9	146.4	144.9	144.2	144.2	144.2	144.9
70°	133.7	133.7	131.5	129.2	126.2	127.0	124.7	122.5	122.5	121.0	121.8
72.5°	111.3	110.5	108.3	107.6	105.3	103.1	101.6	103.1	100.8	100.1	100.8
75°	89.6	88.9	87.4	85.9	86.6	84.4	82.2	81.4	81.4	79.9	79.9
77.5°	68.7	70.2	67.2	66.5	65.0	63.5	62.7	62.0	62.0	62.0	63.5
80°	47.8	48.6	48.6	47.1	47.8	45.6	45.6	45.6	43.3	44.1	44.8
82.5°	30.6	30.6	29.9	30.6	29.9	29.9	29.1	29.1	28.4	28.4	29.1
85°	17.2	16.4	15.7	17.2	16.4	16.4	15.7	15.7	15.7	15.7	15.7
87.5°	3.7	4.5	4.5	4.5	4.5	5.2	5.2	5.2	6.0	6.0	6.0
90°	24.5	23.0	24.5	25.3	26.1	25.3	20.7	15.3	11.5	10.4	9.2
92.5°	57.5	65.9	77.4	98.9	118.1	116.5	90.5	61.3	40.6	36.4	32.2
95°	121.9	154.1	200.9	263.0	300.5	266.0	177.1	110.4	75.1	65.9	56.7
97.5°	250.7	328.1	410.9	493.8	489.9	378.7	235.4	142.6	97.4	87.1	76.7
100°	499.9	604.9	700.0	716.1	605.7	417.1	251.5	157.9	117.3	106.6	95.8
102.5°	816.5	886.3	889.4	798.9	609.5	402.5	252.2	171.7	134.9	124.2	113.5
105°	1028.1	1018.2	931.5	772.1	568.1	382.6	256.1	187.8	151.8	141.0	130.3
107.5°	1090.2	1015.1	886.3	715.3	529.8	371.8	264.5	203.9	168.7	158.0	147.2
110°	1059.6	961.4	824.2	662.4	503.7	368.8	275.2	220.0	186.3	175.2	164.1

TEST NUMBER: P1009140

CATALOG NUMBER: S122DIP-B485D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1004.4	897.8	767.5	625.6	486.9	369.5	286.7	235.4	203.2	191.7	180.2
115°	941.5	841.1	723.0	596.5	475.4	372.6	298.2	251.5	218.5	208.2	197.8
117.5°	885.5	792.0	686.2	576.6	469.2	377.2	310.5	266.0	235.4	224.6	213.9
120°	836.5	755.2	660.1	561.2	463.9	381.8	322.8	281.4	251.5	240.8	230.0
122.5°	800.4	724.5	639.4	548.2	460.8	387.2	333.5	295.9	268.3	257.2	246.1
125°	765.9	698.5	619.5	535.9	457.0	392.5	345.0	310.5	282.9	272.2	261.4
127.5°	736.8	672.4	599.6	524.4	454.7	397.9	355.7	324.3	297.5	286.4	275.2
130°	706.9	646.3	580.4	512.9	453.1	404.0	365.7	336.6	309.7	299.0	288.3
132.5°	676.2	621.8	562.0	503.7	452.4	410.2	375.7	347.3	322.0	311.2	300.5
135°	646.3	595.7	545.1	495.3	451.6	414.8	384.1	357.3	332.7	322.0	311.3
137.5°	616.4	575.0	531.3	489.2	451.6	419.4	391.0	365.7	341.2	331.2	321.2
140°	590.4	555.1	518.3	483.8	450.8	422.5	396.4	372.6	349.6	339.6	329.7
142.5°	566.6	537.5	507.6	478.4	450.8	424.8	401.0	378.0	355.7	346.5	337.3
145°	546.7	522.9	497.6	473.8	449.3	426.3	404.8	383.3	362.6	354.2	345.8
147.5°	529.8	510.6	489.9	469.2	447.0	427.1	407.1	387.9	368.0	360.4	352.7
150°	514.5	498.4	481.5	463.1	444.7	426.3	408.6	391.0	373.4	366.5	359.6
152.5°	501.4	488.4	473.1	457.7	440.9	424.8	409.4	394.1	378.7	372.6	366.5
155°	489.2	477.7	465.4	450.8	436.3	423.2	410.2	397.1	384.1	378.4	372.6
157.5°	476.9	466.9	456.2	444.7	431.7	420.2	410.2	399.4	387.9	383.0	378.0
160°	464.6	456.2	447.8	437.8	427.1	417.9	410.2	401.0	391.8	387.6	383.3
162.5°	453.1	446.2	439.3	431.7	423.2	415.6	409.4	401.7	394.1	391.0	387.9
165°	441.6	436.3	430.9	424.8	417.9	412.5	407.9	402.5	395.6	393.3	391.0
167.5°	430.9	427.1	422.5	417.9	413.3	409.4	407.1	402.5	397.1	395.6	394.1
170°	421.7	418.6	416.3	412.5	409.4	407.1	405.6	401.7	397.9	396.8	395.6
172.5°	413.3	410.9	409.4	407.1	404.8	404.0	403.3	401.0	398.7	397.9	397.1
175°	406.3	405.6	404.8	402.5	401.7	401.0	401.7	400.2	398.7	398.3	397.9
177.5°	401.7	401.0	401.0	399.4	398.7	399.4	401.0	399.4	398.7	398.7	398.7
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P1009140

CATALOG NUMBER: S122DIP-B485D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	971.8	971.8	971.8	971.8
2.5°	953.8	953.8	965.0	977.0
5°	932.9	938.1	956.1	972.5
7.5°	912.8	921.7	944.1	965.0
10°	888.1	900.1	927.7	952.3
12.5°	864.2	875.4	907.5	935.2
15°	830.6	844.8	879.1	913.5
17.5°	797.0	811.2	853.0	893.3
20°	757.4	776.1	823.1	876.9
22.5°	720.8	743.9	796.2	839.6
25°	680.5	716.3	764.9	820.9
27.5°	644.6	680.5	729.8	786.5
30°	604.3	640.9	691.7	743.9
32.5°	565.4	599.0	648.3	712.6
35°	525.1	557.2	605.0	670.0
37.5°	488.5	519.9	572.2	631.9
40°	452.6	485.5	530.3	590.1
42.5°	419.0	448.2	488.5	548.2
45°	388.4	409.3	446.7	502.7
47.5°	356.3	375.0	409.3	465.3
50°	326.4	342.1	372.0	424.3
52.5°	297.3	310.7	338.4	380.2
55°	271.1	283.8	304.0	345.1
57.5°	244.2	254.0	273.4	306.2
60°	218.1	227.1	242.8	269.6
62.5°	192.0	199.4	214.4	236.0
65°	168.8	174.8	186.0	204.7
67.5°	146.4	150.1	159.1	174.0
70°	124.7	127.7	135.2	147.1
72.5°	101.6	104.6	112.8	121.0
75°	82.2	82.9	88.9	95.6
77.5°	64.2	63.5	68.0	73.2
80°	44.1	46.3	50.0	52.3
82.5°	29.9	30.6	32.1	33.6
85°	16.4	17.2	17.2	19.4
87.5°	6.7	7.5	7.5	8.2
90°	7.7	6.1	3.1	0.8
92.5°	26.1	22.2	16.1	11.5
95°	44.5	37.6	29.9	26.8
97.5°	62.9	52.9	44.5	39.9
100°	80.5	68.2	61.3	59.0
102.5°	97.4	85.1	78.2	76.7
105°	113.5	102.0	96.6	93.5
107.5°	130.3	119.6	114.2	111.9
110°	148.0	138.0	133.4	130.3

TEST NUMBER: P1009140

CATALOG NUMBER: S122DIP-B485D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	164.8	155.6	150.3	147.2
115°	182.5	173.3	168.7	164.8
117.5°	199.3	190.9	186.3	183.2
120°	214.7	207.8	203.2	200.1
122.5°	230.8	223.1	218.5	216.2
125°	246.1	236.9	232.3	230.0
127.5°	260.7	250.7	244.6	241.5
130°	272.9	262.2	254.5	251.5
132.5°	284.4	272.9	264.5	260.7
135°	293.6	282.1	272.9	269.9
137.5°	303.6	291.3	282.1	278.3
140°	312.8	300.5	291.3	288.3
142.5°	321.2	309.0	300.5	298.2
145°	330.4	318.9	311.3	308.2
147.5°	339.6	328.9	321.2	318.9
150°	348.1	338.1	332.0	329.7
152.5°	355.7	347.3	341.2	340.4
155°	364.2	355.7	351.1	350.4
157.5°	371.1	363.4	359.6	358.8
160°	377.2	371.1	368.0	367.2
162.5°	382.6	378.0	374.9	375.7
165°	387.2	382.6	381.0	381.8
167.5°	391.0	387.9	386.4	387.2
170°	394.1	391.8	391.0	392.5
172.5°	396.4	394.1	394.8	395.6
175°	397.9	396.4	397.1	397.9
177.5°	398.7	397.1	397.9	399.4
180°	398.7	398.7	398.7	398.7

(END OF REPORT)