

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009185

Luminaire Tested: S122DIP-B485D925UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009185
REPORT IS A COMBINATION OF REPORTS P984393 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D925UB35-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5741.0 lumens
Efficiency: N/A
Efficacy: 109.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009185

CATALOG NUMBER: S122DIP-B485D925UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1009185

CATALOG NUMBER: S122DIP-B485D925UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45
1	95	91	88	84	86	83	80	77	67	65	63	53	52	50	40	39	38
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28
4	73	63	55	49	66	57	51	46	47	42	39	38	34	31	29	26	25
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	17	16
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15383	15383	15383	15383
5°	15419	16401	15478	13049
10°	15240	17905	15336	10758
15°	14871	18885	15077	9062
20°	14638	17732	14638	7877
25°	14172	15233	14236	7044
30°	13404	11974	13659	6380
35°	12724	8280	12937	5837
40°	11943	6252	12079	5404
45°	10979	5138	11158	4937
50°	10147	4510	10163	4520
55°	9196	3842	9254	4066
60°	8181	3210	8296	3549
65°	7277	2610	7408	3031
70°	6370	2049	6535	2445
75°	5348	1487	5555	1772
80°	4176	942	4471	1051
85°	2740	475	2952	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15901 cd/sqm

TEST NUMBER: P1009185

CATALOG NUMBER: S122DIP-B485D925UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.6	1.6
10°-20°	269.4	4.7
20°-30°	391.0	6.8
30°-40°	412.2	7.2
40°-50°	364.7	6.4
50°-60°	291.2	5.1
60°-70°	197.8	3.4
70°-80°	101.2	1.8
80°-90°	27.2	0.5
90°-100°	201.2	3.5
100°-110°	708.4	12.3
110°-120°	744.0	13.0
120°-130°	612.1	10.7
130°-140°	491.7	8.6
140°-150°	371.4	6.5
150°-160°	261.1	4.5
160°-170°	153.7	2.7
170°-180°	50.0	0.9
0°-30°	752.9	13.1
0°-40°	1165.1	20.3
0°-60°	1821.1	31.7
0°-90°	2147.3	37.4
90°-120°	1653.6	28.8
90°-150°	3128.9	54.5
90°-180°	3594.0	62.6
0°-180°	5741.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	972	972	972	972	972	
5°	972	1085	976	864	972	92
15°	914	1334	926	640	914	258
25°	821	1111	825	514	821	375
35°	670	605	681	426	670	419
45°	503	364	511	350	503	390
55°	345	256	347	271	345	308
65°	205	158	208	183	205	203
75°	96	78	99	93	96	103
85°	19	20	21	15	19	23
90°	1	33	1	33	1	3
95°	35	113	35	113	35	36
105°	121	1118	121	1118	121	129
115°	213	1472	213	1472	213	212
125°	298	1194	298	1194	298	265
135°	349	989	349	989	349	270
145°	399	790	399	790	399	250
155°	454	664	454	664	454	209
165°	494	582	494	582	494	139
175°	515	525	515	525	515	49
180°	516	516	516	516	516	

TEST NUMBER: P1009185

CATALOG NUMBER: S122DIP-B485D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	977.0	979.2	983.0	983.7	991.2	997.2	1003.9	1003.9	1006.1	1005.4	999.4
5°	972.5	979.2	988.9	997.2	1010.6	1016.6	1025.5	1032.3	1038.2	1042.7	1042.0
7.5°	965.0	977.0	991.2	1006.9	1024.8	1035.3	1047.9	1059.9	1068.1	1075.6	1080.8
10°	952.3	972.5	991.9	1012.8	1036.0	1050.2	1065.1	1080.8	1093.5	1107.7	1121.1
12.5°	935.2	964.3	988.2	1015.8	1044.2	1059.9	1083.8	1095.8	1120.4	1156.3	1166.0
15°	913.5	953.1	975.5	1010.6	1047.9	1060.6	1093.5	1112.9	1163.7	1186.1	1213.0
17.5°	893.3	937.4	967.3	1007.6	1044.2	1068.9	1101.0	1140.6	1183.1	1215.3	1245.1
20°	876.9	919.5	955.3	1000.1	1046.5	1077.8	1111.4	1159.2	1205.6	1238.4	1261.6
22.5°	839.6	894.1	935.9	986.0	1042.0	1085.3	1117.4	1169.7	1219.7	1239.9	1260.1
25°	820.9	867.9	916.5	973.3	1039.0	1090.5	1118.2	1176.4	1220.5	1228.0	1232.4
27.5°	786.5	839.6	896.3	961.3	1038.2	1081.6	1116.7	1169.7	1204.8	1199.6	1186.1
30°	743.9	808.9	871.7	941.9	1027.8	1074.8	1107.7	1156.3	1174.2	1147.3	1123.4
32.5°	712.6	773.8	843.3	924.7	1015.8	1060.6	1092.8	1130.9	1134.6	1086.0	1045.7
35°	670.0	738.0	816.4	902.3	995.7	1036.0	1065.9	1089.0	1071.1	1003.1	955.3
37.5°	631.9	699.1	782.8	870.2	968.0	1007.6	1031.5	1035.3	991.2	931.4	861.2
40°	590.1	659.5	746.9	838.8	937.4	971.8	986.7	975.5	912.0	842.5	761.1
42.5°	548.2	617.0	711.1	805.2	898.6	927.7	933.7	903.0	825.4	743.9	649.8
45°	502.7	574.4	668.5	763.4	853.7	870.2	870.9	826.9	735.0	649.8	562.4
47.5°	465.3	531.8	625.2	720.0	796.2	807.4	803.0	752.2	652.1	556.5	480.3
50°	424.3	487.7	580.4	673.7	738.7	741.7	730.5	658.0	560.2	472.8	412.3
52.5°	380.2	444.4	529.6	619.2	677.5	673.0	651.3	573.6	481.8	409.3	363.0
55°	345.1	401.9	481.8	569.2	610.2	597.5	573.6	494.5	422.0	360.8	320.4
57.5°	306.2	356.3	434.7	510.9	534.8	522.9	499.0	425.0	357.8	311.5	284.6
60°	269.6	315.2	383.9	447.4	466.1	453.4	425.8	359.3	310.7	271.9	251.7
62.5°	236.0	275.6	333.1	391.4	398.9	386.2	362.3	308.5	266.7	236.0	221.1
65°	204.7	242.0	288.3	332.4	339.1	325.7	301.0	262.2	227.1	207.6	193.5
67.5°	174.0	203.9	245.0	277.1	280.8	268.1	248.0	216.6	194.9	174.0	163.6
70°	147.1	169.6	201.7	227.8	229.3	217.4	206.9	178.5	162.1	147.1	138.9
72.5°	121.0	136.7	161.3	180.8	181.5	174.0	164.3	146.4	132.2	121.8	113.5
75°	95.6	109.1	124.0	141.2	140.4	134.4	127.0	115.8	103.8	97.1	93.4
77.5°	73.2	81.4	93.4	104.6	104.6	101.6	97.1	88.9	81.4	74.7	71.0
80°	52.3	57.5	67.2	71.0	72.5	71.7	68.0	62.0	59.0	53.8	52.3
82.5°	33.6	37.3	41.8	45.6	47.8	46.3	45.6	42.6	38.1	36.6	35.1
85°	19.4	20.9	23.2	25.4	26.1	25.4	26.9	24.6	22.4	22.4	21.7
87.5°	8.2	9.0	10.5	10.5	11.2	11.2	10.5	11.2	11.2	10.5	9.7
90°	1.0	4.0	7.9	9.9	11.9	13.4	14.9	19.8	26.8	32.7	33.7
92.5°	14.9	20.8	28.8	33.7	41.7	47.2	52.6	79.4	117.1	150.8	152.8
95°	34.7	38.7	48.6	57.6	73.4	85.4	97.3	142.9	229.2	344.4	389.0
97.5°	51.6	57.6	68.5	81.4	99.2	112.6	126.0	184.6	304.7	490.2	634.1
100°	76.4	79.4	88.3	104.2	124.0	137.9	151.8	204.4	325.5	539.9	784.0
102.5°	99.2	101.2	110.2	126.0	146.9	160.8	174.7	222.3	326.5	521.0	788.9
105°	121.1	125.0	132.0	146.9	168.7	182.6	196.5	243.1	331.5	495.2	735.4
107.5°	144.9	147.9	154.8	168.7	190.5	204.4	218.3	264.0	342.4	481.3	685.7
110°	168.7	172.7	178.6	191.5	212.4	226.8	241.1	284.8	356.3	477.3	652.0

TEST NUMBER: P1009185

CATALOG NUMBER: S122DIP-B485D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	190.5	194.5	201.5	213.4	233.2	248.1	263.0	304.7	371.1	478.3	630.2
115°	213.4	218.3	224.3	236.2	256.0	269.4	282.8	325.5	386.0	482.3	615.3
117.5°	237.2	241.1	247.1	258.0	276.9	290.8	304.7	344.4	401.9	488.2	607.3
120°	259.0	263.0	268.9	277.9	297.7	311.6	325.5	364.2	417.8	494.2	600.4
122.5°	279.8	282.8	288.8	298.7	318.6	333.0	347.3	383.1	431.7	501.1	596.4
125°	297.7	300.7	306.6	318.6	338.4	352.3	366.2	401.9	446.6	508.1	591.5
127.5°	312.6	316.6	324.5	337.4	356.3	370.6	385.0	419.8	460.5	515.0	588.5
130°	325.5	329.5	339.4	353.3	373.1	387.0	400.9	435.7	473.4	523.0	586.5
132.5°	337.4	342.4	353.3	368.2	389.0	402.9	416.8	449.5	486.3	530.9	585.5
135°	349.3	353.3	365.2	380.1	402.9	416.8	430.7	462.4	497.2	536.9	584.5
137.5°	360.2	365.2	377.1	393.0	415.8	428.7	441.6	473.4	506.1	542.8	584.5
140°	373.1	377.1	389.0	404.9	426.7	439.6	452.5	482.3	513.1	546.8	583.5
142.5°	386.0	389.0	399.9	415.8	436.6	448.6	460.5	489.2	519.0	549.8	583.5
145°	398.9	402.9	412.8	427.7	447.6	458.5	469.4	496.2	524.0	551.8	581.5
147.5°	412.8	415.8	425.7	439.6	456.5	466.4	476.3	502.1	527.0	552.8	578.6
150°	426.7	429.7	437.6	450.5	465.4	474.4	483.3	506.1	528.9	551.8	575.6
152.5°	440.6	441.6	449.5	460.5	474.4	482.3	490.2	510.1	529.9	549.8	570.6
155°	453.5	454.5	460.5	471.4	482.3	489.8	497.2	514.1	530.9	547.8	564.7
157.5°	464.4	465.4	470.4	480.3	489.2	495.6	502.1	517.0	530.9	543.8	558.7
160°	475.3	476.3	480.3	488.2	496.2	501.6	507.1	519.0	530.9	540.8	552.8
162.5°	486.3	485.3	489.2	495.2	502.1	506.1	510.1	520.0	529.9	537.9	547.8
165°	494.2	493.2	495.2	501.1	506.1	509.1	512.1	521.0	527.9	533.9	540.8
167.5°	501.1	500.2	502.1	506.1	510.1	512.1	514.1	521.0	527.0	529.9	534.9
170°	508.1	506.1	507.1	510.1	512.1	513.6	515.0	520.0	525.0	527.0	529.9
172.5°	512.1	511.1	510.1	513.1	514.1	515.0	516.0	519.0	522.0	523.0	524.0
175°	515.0	514.1	513.1	515.0	515.0	515.5	516.0	518.0	520.0	519.0	520.0
177.5°	517.0	515.0	514.1	516.0	516.0	516.0	516.0	517.0	519.0	517.0	516.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P1009185

CATALOG NUMBER: S122DIP-B485D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	1009.9	1010.6	1012.1	1019.6	1023.3	1024.0	1021.1	1027.8	1030.0	1027.8	1026.3
5°	1057.7	1062.1	1071.1	1080.8	1080.1	1080.8	1085.3	1089.8	1091.3	1085.3	1087.5
7.5°	1099.5	1108.4	1118.2	1133.1	1133.1	1140.6	1143.6	1147.3	1156.3	1151.8	1150.3
10°	1147.3	1159.2	1177.2	1201.1	1201.8	1209.3	1216.8	1228.7	1232.4	1229.5	1230.9
12.5°	1207.0	1230.2	1231.7	1257.8	1269.8	1271.3	1283.2	1281.0	1288.5	1288.5	1301.2
15°	1233.2	1269.0	1289.2	1314.6	1322.1	1313.1	1322.8	1333.3	1334.0	1334.0	1333.3
17.5°	1280.2	1294.4	1314.6	1328.0	1331.0	1331.0	1331.8	1336.3	1333.3	1327.3	1331.8
20°	1290.0	1295.9	1303.4	1301.9	1303.4	1295.9	1288.5	1281.0	1281.7	1278.0	1289.2
22.5°	1272.0	1270.5	1253.4	1242.2	1242.2	1227.2	1213.0	1206.3	1199.6	1201.8	1205.6
25°	1227.2	1204.1	1183.1	1166.7	1163.0	1139.1	1119.7	1113.7	1102.5	1111.4	1112.9
27.5°	1155.5	1129.4	1095.8	1081.6	1062.1	1052.4	1039.0	1021.1	997.9	1011.3	1009.1
30°	1078.6	1039.7	1012.1	977.7	947.1	944.9	919.5	889.6	877.6	877.6	884.4
32.5°	992.7	941.1	900.8	852.3	822.4	809.7	779.1	749.2	755.9	733.5	741.7
35°	892.6	824.6	773.8	726.8	704.4	689.4	649.8	633.4	615.5	605.0	624.4
37.5°	797.0	718.6	653.6	602.0	593.8	566.9	540.0	529.6	519.1	523.6	522.9
40°	680.5	611.0	552.7	512.4	498.2	485.5	467.6	454.9	448.2	451.9	452.6
42.5°	575.1	516.9	473.6	445.2	433.2	424.3	415.3	404.8	402.6	402.6	405.6
45°	493.7	445.9	416.8	393.6	386.9	380.2	373.5	369.0	367.5	364.5	366.7
47.5°	428.7	390.6	372.7	355.5	348.1	346.6	340.6	338.4	335.4	334.6	335.4
50°	374.2	350.3	333.9	324.2	318.9	316.7	313.7	309.2	307.7	311.5	310.0
52.5°	336.1	313.7	304.7	295.0	292.1	289.1	284.6	285.3	284.6	283.1	283.1
55°	298.0	283.8	274.9	267.4	266.7	263.7	259.9	258.4	257.7	256.2	258.4
57.5°	267.4	256.2	248.0	241.3	238.3	238.3	234.5	231.5	231.5	230.8	231.5
60°	236.8	225.6	220.3	213.6	211.4	210.6	208.4	206.9	204.7	204.7	204.7
62.5°	208.4	199.4	193.5	187.5	188.2	184.5	181.5	180.0	180.0	180.8	180.8
65°	181.5	175.5	168.1	162.8	161.3	160.6	159.1	158.3	156.1	157.6	157.6
67.5°	156.9	148.6	144.2	141.9	139.7	138.9	137.4	135.9	135.2	134.4	135.9
70°	132.2	125.5	121.8	120.3	118.0	117.3	116.5	114.3	115.0	115.8	116.5
72.5°	109.8	103.8	103.1	98.6	98.6	98.6	95.6	97.1	96.4	94.9	96.4
75°	86.6	83.7	82.2	79.9	80.7	79.9	79.2	76.9	76.9	77.7	78.4
77.5°	68.7	65.7	65.0	62.7	61.2	62.7	61.2	60.5	60.5	61.2	61.2
80°	50.8	49.3	47.1	47.1	47.1	46.3	46.3	46.3	45.6	44.8	45.6
82.5°	33.6	33.6	32.9	32.1	32.9	31.4	32.1	32.1	32.1	32.1	32.1
85°	21.7	20.9	20.9	20.2	20.2	20.2	20.9	19.4	19.4	20.2	20.2
87.5°	9.7	9.7	9.7	10.5	9.7	9.7	9.7	10.5	9.7	9.7	9.7
90°	32.7	31.8	29.8	31.8	32.2	32.7	32.7	32.7	32.7	32.7	32.7
92.5°	128.0	100.2	85.3	74.4	70.4	66.5	65.5	61.5	62.5	60.5	62.5
95°	340.4	260.0	199.5	157.8	146.9	136.0	123.1	115.1	112.1	113.1	112.1
97.5°	639.1	531.9	424.7	324.5	294.8	265.0	226.3	206.4	195.5	189.5	195.5
100°	926.9	906.0	783.0	647.0	587.0	527.0	444.6	401.9	373.1	355.3	373.1
102.5°	1034.1	1151.2	1147.2	1056.9	992.4	927.9	836.6	756.2	718.5	692.7	718.5
105°	999.3	1205.7	1317.9	1330.8	1314.4	1298.0	1236.5	1175.0	1132.3	1118.4	1132.3
107.5°	925.9	1147.2	1313.9	1411.2	1431.1	1450.9	1449.9	1440.9	1428.0	1405.2	1428.0
110°	857.4	1066.8	1244.4	1371.5	1412.2	1452.8	1495.5	1514.4	1523.3	1522.3	1523.3

TEST NUMBER: P1009185

CATALOG NUMBER: S122DIP-B485D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	809.8	993.4	1162.1	1300.0	1348.2	1396.3	1459.8	1494.5	1513.4	1520.3	1513.4
115°	772.1	935.8	1088.6	1218.6	1269.8	1320.9	1391.3	1437.0	1462.8	1471.7	1462.8
117.5°	746.3	888.2	1025.1	1146.2	1194.8	1243.4	1315.9	1364.5	1391.3	1398.3	1391.3
120°	726.4	854.4	977.5	1082.7	1127.8	1173.0	1242.5	1289.1	1317.9	1327.8	1317.9
122.5°	709.5	827.6	937.8	1036.0	1075.7	1115.4	1176.0	1221.6	1246.4	1254.4	1246.4
125°	693.7	801.8	904.1	991.4	1028.6	1065.8	1123.4	1161.1	1185.9	1193.8	1185.9
127.5°	678.8	776.0	870.3	953.7	988.4	1023.1	1073.8	1109.5	1131.3	1137.3	1131.3
130°	663.9	751.2	836.6	915.0	947.8	980.5	1029.1	1062.8	1082.7	1090.6	1082.7
132.5°	652.0	727.4	804.8	875.3	905.6	935.8	983.4	1017.2	1035.0	1042.0	1035.0
135°	641.1	705.6	771.1	836.6	864.4	892.1	934.8	967.6	985.4	989.4	985.4
137.5°	633.1	687.7	744.3	797.9	822.7	847.5	888.2	917.0	932.8	938.8	932.8
140°	626.2	670.8	718.5	764.1	786.0	807.8	839.5	865.4	880.2	886.2	880.2
142.5°	619.2	657.0	695.7	733.4	750.8	768.1	797.9	820.7	833.6	833.6	833.6
145°	613.3	644.1	676.8	707.6	722.0	736.3	760.2	777.0	787.0	789.9	787.0
147.5°	607.3	634.1	660.9	685.7	696.7	707.6	728.4	742.3	749.2	751.2	749.2
150°	599.4	623.2	645.0	665.9	674.8	683.7	698.6	710.5	716.5	717.5	716.5
152.5°	592.4	612.3	632.1	649.0	656.4	663.9	674.8	684.7	688.7	688.7	688.7
155°	583.5	602.4	618.2	633.1	638.6	644.1	655.0	661.9	665.9	663.9	665.9
157.5°	575.6	590.5	604.4	617.3	621.8	626.2	634.1	640.1	642.1	642.1	642.1
160°	566.6	579.5	590.5	601.4	604.8	608.3	615.3	620.2	621.2	621.2	621.2
162.5°	558.7	568.6	577.6	586.5	589.0	591.5	598.4	601.4	602.4	601.4	602.4
165°	549.8	557.7	564.7	571.6	573.6	575.6	579.5	583.5	583.5	582.5	583.5
167.5°	540.8	546.8	552.8	557.7	559.7	561.7	563.7	565.7	565.7	564.7	565.7
170°	533.9	538.9	541.8	545.8	546.8	547.8	548.8	551.8	550.8	548.8	550.8
172.5°	527.0	529.9	531.9	534.9	535.4	535.9	536.9	537.9	536.9	535.9	536.9
175°	521.0	524.0	525.0	526.0	526.5	527.0	527.0	527.9	527.0	525.0	527.0
177.5°	517.0	519.0	519.0	520.0	520.0	520.0	520.0	520.0	519.0	517.0	519.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P1009185

CATALOG NUMBER: S122DIP-B485D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	1030.0	1024.8	1020.3	1021.1	1024.8	1021.8	1014.3	1004.6	1000.9	996.4	1000.9
5°	1092.0	1087.5	1078.6	1079.3	1077.1	1074.1	1062.1	1047.2	1047.2	1035.3	1033.8
7.5°	1153.3	1146.5	1140.6	1139.1	1130.9	1124.9	1114.4	1093.5	1085.3	1071.1	1062.9
10°	1222.0	1216.8	1210.0	1201.8	1197.3	1186.9	1169.7	1139.1	1124.1	1104.7	1090.5
12.5°	1291.4	1290.7	1275.8	1259.3	1258.6	1242.2	1230.2	1189.1	1169.0	1142.8	1109.2
15°	1335.5	1331.8	1323.6	1315.4	1317.6	1299.7	1272.8	1224.2	1210.8	1179.4	1143.6
17.5°	1334.8	1334.8	1332.5	1331.0	1328.8	1323.6	1308.6	1276.5	1254.8	1215.3	1181.6
20°	1292.2	1301.9	1304.1	1303.4	1310.9	1314.6	1313.9	1293.7	1276.5	1241.4	1207.0
22.5°	1207.0	1229.5	1239.2	1245.1	1260.8	1269.0	1288.5	1281.0	1276.5	1250.4	1221.2
25°	1127.9	1135.3	1164.5	1166.0	1187.6	1207.8	1227.2	1239.9	1256.3	1246.6	1222.0
27.5°	1025.5	1042.7	1063.6	1079.3	1083.8	1124.9	1157.0	1180.9	1218.2	1221.2	1213.0
30°	909.8	918.0	952.3	973.3	997.2	1027.0	1073.3	1114.4	1148.0	1178.7	1189.1
32.5°	768.6	802.2	822.4	847.8	868.7	921.7	978.5	1031.5	1070.4	1121.9	1144.3
35°	639.4	665.5	699.9	710.3	748.4	793.2	867.2	935.2	994.2	1046.5	1092.0
37.5°	532.6	553.5	590.1	606.5	628.9	686.4	748.4	832.8	903.8	968.0	1024.8
40°	459.4	475.0	502.7	507.9	526.6	578.9	628.9	708.1	802.2	888.9	950.8
42.5°	409.3	416.8	435.5	442.2	454.1	489.2	534.1	608.8	696.1	785.8	873.2
45°	373.5	378.7	389.9	395.9	410.8	426.5	463.1	522.9	591.6	682.0	776.1
47.5°	341.3	348.1	352.6	356.3	364.5	381.7	405.6	449.7	515.4	598.3	689.4
50°	314.5	316.7	324.9	325.7	330.9	342.1	364.5	391.4	443.7	510.9	599.0
52.5°	287.6	289.8	295.0	300.3	302.5	311.5	326.4	348.8	387.7	440.7	519.1
55°	260.7	263.7	268.9	272.6	274.9	282.3	291.3	313.0	343.6	380.9	445.2
57.5°	233.8	240.5	242.0	244.2	248.0	256.2	264.4	277.1	301.0	335.4	382.4
60°	208.4	210.6	215.9	218.1	221.8	226.3	236.8	246.5	263.7	290.6	333.1
62.5°	182.3	187.5	189.7	192.0	194.9	200.2	206.9	217.4	232.3	254.0	287.6
65°	159.8	160.6	165.1	168.1	171.0	174.8	181.5	191.2	200.2	220.3	245.0
67.5°	138.2	139.7	141.2	144.2	147.9	151.6	157.6	162.8	174.0	187.5	206.9
70°	117.3	117.3	121.0	123.2	122.5	127.0	131.5	137.4	145.7	158.3	174.0
72.5°	98.6	97.8	100.8	101.6	103.1	106.1	109.1	115.0	119.5	129.2	141.2
75°	78.4	79.9	81.4	81.4	83.7	85.9	88.9	91.9	97.1	103.1	112.0
77.5°	62.0	62.0	63.5	64.2	66.5	65.7	68.7	71.7	75.4	80.7	87.4
80°	45.6	47.1	47.1	47.1	47.8	48.6	51.5	53.8	56.0	59.8	62.7
82.5°	32.1	32.1	33.6	33.6	33.6	35.1	35.1	35.9	37.3	39.6	41.8
85°	20.2	20.2	20.2	20.9	20.2	20.9	22.4	21.7	22.4	23.9	23.9
87.5°	9.7	9.7	9.7	9.7	9.7	10.5	9.7	10.5	11.2	11.2	11.2
90°	32.7	32.7	32.7	32.2	31.8	29.8	31.8	32.7	33.7	32.7	26.8
92.5°	61.5	65.5	66.5	70.4	74.4	85.3	100.2	128.0	152.8	150.8	117.1
95°	115.1	123.1	136.0	146.9	157.8	199.5	260.0	340.4	389.0	344.4	229.2
97.5°	206.4	226.3	265.0	294.8	324.5	424.7	531.9	639.1	634.1	490.2	304.7
100°	401.9	444.6	527.0	587.0	647.0	783.0	906.0	926.9	784.0	539.9	325.5
102.5°	756.2	836.6	927.9	992.4	1056.9	1147.2	1151.2	1034.1	788.9	521.0	326.5
105°	1175.0	1236.5	1298.0	1314.4	1330.8	1317.9	1205.7	999.3	735.4	495.2	331.5
107.5°	1440.9	1449.9	1450.9	1431.1	1411.2	1313.9	1147.2	925.9	685.7	481.3	342.4
110°	1514.4	1495.5	1452.8	1412.2	1371.5	1244.4	1066.8	857.4	652.0	477.3	356.3

TEST NUMBER: P1009185

CATALOG NUMBER: S122DIP-B485D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1494.5	1459.8	1396.3	1348.2	1300.0	1162.1	993.4	809.8	630.2	478.3	371.1
115°	1437.0	1391.3	1320.9	1269.8	1218.6	1088.6	935.8	772.1	615.3	482.3	386.0
117.5°	1364.5	1315.9	1243.4	1194.8	1146.2	1025.1	888.2	746.3	607.3	488.2	401.9
120°	1289.1	1242.5	1173.0	1127.8	1082.7	977.5	854.4	726.4	600.4	494.2	417.8
122.5°	1221.6	1176.0	1115.4	1075.7	1036.0	937.8	827.6	709.5	596.4	501.1	431.7
125°	1161.1	1123.4	1065.8	1028.6	991.4	904.1	801.8	693.7	591.5	508.1	446.6
127.5°	1109.5	1073.8	1023.1	988.4	953.7	870.3	776.0	678.8	588.5	515.0	460.5
130°	1062.8	1029.1	980.5	947.8	915.0	836.6	751.2	663.9	586.5	523.0	473.4
132.5°	1017.2	983.4	935.8	905.6	875.3	804.8	727.4	652.0	585.5	530.9	486.3
135°	967.6	934.8	892.1	864.4	836.6	771.1	705.6	641.1	584.5	536.9	497.2
137.5°	917.0	888.2	847.5	822.7	797.9	744.3	687.7	633.1	584.5	542.8	506.1
140°	865.4	839.5	807.8	786.0	764.1	718.5	670.8	626.2	583.5	546.8	513.1
142.5°	820.7	797.9	768.1	750.8	733.4	695.7	657.0	619.2	583.5	549.8	519.0
145°	777.0	760.2	736.3	722.0	707.6	676.8	644.1	613.3	581.5	551.8	524.0
147.5°	742.3	728.4	707.6	696.7	685.7	660.9	634.1	607.3	578.6	552.8	527.0
150°	710.5	698.6	683.7	674.8	665.9	645.0	623.2	599.4	575.6	551.8	528.9
152.5°	684.7	674.8	663.9	656.4	649.0	632.1	612.3	592.4	570.6	549.8	529.9
155°	661.9	655.0	644.1	638.6	633.1	618.2	602.4	583.5	564.7	547.8	530.9
157.5°	640.1	634.1	626.2	621.8	617.3	604.4	590.5	575.6	558.7	543.8	530.9
160°	620.2	615.3	608.3	604.8	601.4	590.5	579.5	566.6	552.8	540.8	530.9
162.5°	601.4	598.4	591.5	589.0	586.5	577.6	568.6	558.7	547.8	537.9	529.9
165°	583.5	579.5	575.6	573.6	571.6	564.7	557.7	549.8	540.8	533.9	527.9
167.5°	565.7	563.7	561.7	559.7	557.7	552.8	546.8	540.8	534.9	529.9	527.0
170°	551.8	548.8	547.8	546.8	545.8	541.8	538.9	533.9	529.9	527.0	525.0
172.5°	537.9	536.9	535.9	535.4	534.9	531.9	529.9	527.0	524.0	523.0	522.0
175°	527.9	527.0	527.0	526.5	526.0	525.0	524.0	521.0	520.0	519.0	520.0
177.5°	520.0	520.0	520.0	520.0	520.0	519.0	519.0	517.0	516.0	517.0	519.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P1009185

CATALOG NUMBER: S122DIP-B485D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	997.2	993.4	991.2	992.7	988.2	977.0	977.0	980.7	976.2	971.8	965.0
5°	1024.8	1017.3	1012.8	1012.1	1001.6	983.7	980.0	976.2	966.5	956.1	944.9
7.5°	1051.7	1038.2	1030.8	1025.5	1010.6	987.4	977.7	969.5	953.8	938.1	924.0
10°	1074.1	1054.7	1045.7	1037.5	1018.1	988.9	973.3	958.3	938.1	918.0	900.1
12.5°	1092.0	1069.6	1058.4	1046.5	1022.6	984.5	965.0	941.1	921.0	894.1	876.2
15°	1121.9	1075.6	1065.1	1053.9	1029.3	977.0	953.1	926.2	898.6	862.7	843.3
17.5°	1145.8	1083.8	1083.1	1059.2	1027.0	974.0	937.4	902.3	872.4	836.6	805.9
20°	1160.0	1096.5	1084.5	1059.9	1019.6	953.8	915.7	876.9	844.8	801.5	770.8
22.5°	1171.9	1114.4	1083.1	1053.2	1003.9	947.1	891.1	854.5	810.4	763.4	734.2
25°	1176.4	1118.2	1085.3	1050.9	992.7	927.7	864.2	824.6	775.3	732.7	693.2
27.5°	1177.2	1117.4	1077.1	1041.2	977.0	902.3	837.3	795.5	741.0	691.7	652.1
30°	1169.7	1109.2	1072.6	1033.8	962.1	879.1	804.4	758.1	699.9	650.6	609.5
32.5°	1147.3	1092.8	1062.9	1020.3	942.6	847.0	773.1	721.5	660.3	611.7	572.2
35°	1109.9	1072.6	1039.7	1000.1	917.2	817.1	741.7	681.2	619.2	572.9	535.6
37.5°	1063.6	1043.5	1012.8	974.0	888.1	790.3	706.6	639.4	577.4	532.6	496.0
40°	1000.9	1006.1	976.2	941.1	853.7	753.7	661.0	596.8	538.5	496.7	460.9
42.5°	932.9	954.6	937.4	903.8	815.7	713.3	627.4	556.5	499.7	456.4	426.5
45°	859.7	897.1	886.6	862.0	776.1	670.7	579.6	510.9	460.9	419.0	392.9
47.5°	779.8	832.8	832.8	814.9	732.0	628.2	538.5	468.3	419.0	389.2	363.8
50°	698.4	758.1	767.8	755.9	682.7	579.6	488.5	425.0	382.4	353.3	334.6
52.5°	613.2	682.7	700.6	694.6	630.4	533.3	447.4	385.4	346.6	321.2	304.7
55°	531.8	612.5	631.9	634.1	574.4	482.5	401.9	347.3	310.0	292.8	278.6
57.5°	454.9	532.6	554.2	558.0	517.6	436.2	359.3	311.5	277.9	263.7	252.5
60°	389.2	454.1	482.5	490.7	455.6	382.4	319.7	273.4	248.0	234.5	224.1
62.5°	335.4	387.7	417.5	419.8	404.1	335.4	278.6	239.8	218.1	206.2	200.9
65°	283.1	330.1	348.1	357.0	344.3	290.6	240.5	208.4	191.2	180.8	175.5
67.5°	241.3	271.1	286.1	298.0	285.3	245.0	204.7	178.5	165.8	155.4	152.4
70°	197.9	222.6	233.8	245.7	234.5	203.9	174.8	150.9	139.7	131.5	127.7
72.5°	158.3	177.8	188.2	195.7	189.0	163.6	139.7	123.2	115.0	109.1	106.8
75°	125.5	138.9	144.9	150.1	147.1	127.7	112.8	99.3	91.9	86.6	85.2
77.5°	95.6	105.3	112.0	113.5	109.8	97.1	84.4	76.2	70.2	67.2	65.7
80°	68.0	73.9	77.7	79.9	76.2	71.0	62.0	56.0	50.8	47.1	46.3
82.5°	45.6	48.6	51.5	50.8	49.3	44.8	39.6	36.6	34.4	31.4	31.4
85°	26.1	26.9	28.4	29.1	28.4	25.4	22.4	20.9	19.4	17.2	17.2
87.5°	11.2	12.0	12.0	12.7	11.2	11.2	9.7	8.2	8.2	7.5	6.7
90°	19.8	14.9	13.4	11.9	9.9	7.9	4.0	1.0	4.0	7.9	9.9
92.5°	79.4	52.6	47.2	41.7	33.7	28.8	20.8	14.9	20.8	28.8	33.7
95°	142.9	97.3	85.4	73.4	57.6	48.6	38.7	34.7	38.7	48.6	57.6
97.5°	184.6	126.0	112.6	99.2	81.4	68.5	57.6	51.6	57.6	68.5	81.4
100°	204.4	151.8	137.9	124.0	104.2	88.3	79.4	76.4	79.4	88.3	104.2
102.5°	222.3	174.7	160.8	146.9	126.0	110.2	101.2	99.2	101.2	110.2	126.0
105°	243.1	196.5	182.6	168.7	146.9	132.0	125.0	121.1	125.0	132.0	146.9
107.5°	264.0	218.3	204.4	190.5	168.7	154.8	147.9	144.9	147.9	154.8	168.7
110°	284.8	241.1	226.8	212.4	191.5	178.6	172.7	168.7	172.7	178.6	191.5

TEST NUMBER: P1009185

CATALOG NUMBER: S122DIP-B485D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	304.7	263.0	248.1	233.2	213.4	201.5	194.5	190.5	194.5	201.5	213.4
115°	325.5	282.8	269.4	256.0	236.2	224.3	218.3	213.4	218.3	224.3	236.2
117.5°	344.4	304.7	290.8	276.9	258.0	247.1	241.1	237.2	241.1	247.1	258.0
120°	364.2	325.5	311.6	297.7	277.9	268.9	263.0	259.0	263.0	268.9	277.9
122.5°	383.1	347.3	333.0	318.6	298.7	288.8	282.8	279.8	282.8	288.8	298.7
125°	401.9	366.2	352.3	338.4	318.6	306.6	300.7	297.7	300.7	306.6	318.6
127.5°	419.8	385.0	370.6	356.3	337.4	324.5	316.6	312.6	316.6	324.5	337.4
130°	435.7	400.9	387.0	373.1	353.3	339.4	329.5	325.5	329.5	339.4	353.3
132.5°	449.5	416.8	402.9	389.0	368.2	353.3	342.4	337.4	342.4	353.3	368.2
135°	462.4	430.7	416.8	402.9	380.1	365.2	353.3	349.3	353.3	365.2	380.1
137.5°	473.4	441.6	428.7	415.8	393.0	377.1	365.2	360.2	365.2	377.1	393.0
140°	482.3	452.5	439.6	426.7	404.9	389.0	377.1	373.1	377.1	389.0	404.9
142.5°	489.2	460.5	448.6	436.6	415.8	399.9	389.0	386.0	389.0	399.9	415.8
145°	496.2	469.4	458.5	447.6	427.7	412.8	402.9	398.9	402.9	412.8	427.7
147.5°	502.1	476.3	466.4	456.5	439.6	425.7	415.8	412.8	415.8	425.7	439.6
150°	506.1	483.3	474.4	465.4	450.5	437.6	429.7	426.7	429.7	437.6	450.5
152.5°	510.1	490.2	482.3	474.4	460.5	449.5	441.6	440.6	441.6	449.5	460.5
155°	514.1	497.2	489.8	482.3	471.4	460.5	454.5	453.5	454.5	460.5	471.4
157.5°	517.0	502.1	495.6	489.2	480.3	470.4	465.4	464.4	465.4	470.4	480.3
160°	519.0	507.1	501.6	496.2	488.2	480.3	476.3	475.3	476.3	480.3	488.2
162.5°	520.0	510.1	506.1	502.1	495.2	489.2	485.3	486.3	485.3	489.2	495.2
165°	521.0	512.1	509.1	506.1	501.1	495.2	493.2	494.2	493.2	495.2	501.1
167.5°	521.0	514.1	512.1	510.1	506.1	502.1	500.2	501.1	500.2	502.1	506.1
170°	520.0	515.0	513.6	512.1	510.1	507.1	506.1	508.1	506.1	507.1	510.1
172.5°	519.0	516.0	515.0	514.1	513.1	510.1	511.1	512.1	511.1	510.1	513.1
175°	518.0	516.0	515.5	515.0	515.0	513.1	514.1	515.0	514.1	513.1	515.0
177.5°	517.0	516.0	516.0	516.0	516.0	514.1	515.0	517.0	515.0	514.1	516.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P1009185

CATALOG NUMBER: S122DIP-B485D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	961.3	965.0	964.3	956.8	948.6	941.9	929.2	930.7	926.2	926.9	931.4
5°	937.4	937.4	934.4	924.0	910.5	903.0	888.9	885.1	876.2	875.4	874.7
7.5°	912.0	908.3	904.5	889.6	873.2	861.2	841.8	837.3	828.3	822.4	819.4
10°	882.1	876.9	869.4	852.3	832.1	817.1	797.0	791.0	773.8	766.4	761.9
12.5°	849.3	846.3	834.3	820.1	787.3	770.8	741.7	747.7	730.5	715.6	713.3
15°	816.4	805.2	798.5	775.3	735.7	728.3	705.1	693.2	677.5	665.5	665.5
17.5°	784.3	767.1	752.2	727.5	698.4	677.5	660.3	654.3	634.9	622.9	620.7
20°	741.7	722.3	718.6	683.4	663.3	640.1	623.7	608.8	594.6	589.3	585.6
22.5°	701.4	679.0	673.0	643.1	622.9	599.8	583.4	572.9	562.4	558.7	552.0
25°	658.0	644.6	635.6	603.5	581.1	559.5	548.2	540.8	531.1	530.3	525.8
27.5°	616.2	603.5	594.6	563.9	547.5	527.3	518.4	510.2	504.9	502.7	500.4
30°	580.4	566.2	555.7	533.3	513.1	496.7	489.2	484.0	481.0	477.3	476.5
32.5°	540.8	532.6	518.4	501.2	485.5	469.8	465.3	461.6	457.1	455.6	454.9
35°	507.2	496.0	487.0	467.6	460.9	447.4	442.2	439.2	433.2	431.7	430.2
37.5°	474.3	463.8	454.1	442.2	429.5	422.0	419.0	414.5	411.6	412.3	410.8
40°	441.4	433.2	425.8	413.1	405.6	401.9	395.9	391.4	389.9	390.6	389.9
42.5°	409.3	401.9	397.4	387.7	380.2	376.5	372.7	368.2	370.5	370.5	372.7
45°	380.2	373.5	370.5	363.0	358.5	352.6	348.8	348.1	351.1	350.3	350.3
47.5°	350.3	348.1	344.3	337.6	331.6	327.9	327.2	327.2	330.1	331.6	330.9
50°	327.2	322.7	318.2	313.0	308.5	307.0	304.7	306.2	309.2	309.2	310.7
52.5°	298.0	295.0	293.5	289.1	286.1	286.1	286.1	286.8	289.1	291.3	290.6
55°	272.6	270.4	268.9	266.7	262.9	263.7	262.9	264.4	266.7	268.9	270.4
57.5°	245.7	245.0	243.5	239.8	239.8	239.0	241.3	242.0	245.7	247.2	249.5
60°	221.8	219.6	219.6	216.6	216.6	216.6	218.9	221.1	224.1	224.8	226.3
62.5°	196.4	196.4	195.7	193.5	193.5	195.7	196.4	199.4	200.9	200.9	203.2
65°	172.5	171.8	171.0	171.8	172.5	172.5	174.8	176.3	177.8	178.5	179.3
67.5°	148.6	147.9	149.4	148.6	150.1	153.1	152.4	154.6	156.9	156.9	157.6
70°	126.2	127.7	127.0	128.5	127.7	129.2	131.5	132.2	132.2	133.0	135.2
72.5°	105.3	105.3	105.3	104.6	105.3	106.8	108.3	109.1	110.5	111.3	113.5
75°	85.2	85.2	83.7	85.2	85.2	86.6	88.1	88.1	88.1	89.6	91.9
77.5°	64.2	65.0	64.2	65.7	65.7	66.5	68.0	67.2	68.7	69.5	70.2
80°	47.1	46.3	46.3	46.3	47.1	47.1	48.6	49.3	49.3	51.5	50.0
82.5°	29.9	30.6	29.9	30.6	30.6	31.4	30.6	31.4	32.1	33.6	32.9
85°	17.2	16.4	16.4	17.2	16.4	16.4	17.2	16.4	17.2	16.4	17.2
87.5°	6.7	6.0	6.0	6.0	6.0	5.2	5.2	4.5	4.5	4.5	3.7
90°	11.9	13.4	14.9	19.8	26.8	32.7	33.7	32.7	31.8	29.8	31.8
92.5°	41.7	47.2	52.6	79.4	117.1	150.8	152.8	128.0	100.2	85.3	74.4
95°	73.4	85.4	97.3	142.9	229.2	344.4	389.0	340.4	260.0	199.5	157.8
97.5°	99.2	112.6	126.0	184.6	304.7	490.2	634.1	639.1	531.9	424.7	324.5
100°	124.0	137.9	151.8	204.4	325.5	539.9	784.0	926.9	906.0	783.0	647.0
102.5°	146.9	160.8	174.7	222.3	326.5	521.0	788.9	1034.1	1151.2	1147.2	1056.9
105°	168.7	182.6	196.5	243.1	331.5	495.2	735.4	999.3	1205.7	1317.9	1330.8
107.5°	190.5	204.4	218.3	264.0	342.4	481.3	685.7	925.9	1147.2	1313.9	1411.2
110°	212.4	226.8	241.1	284.8	356.3	477.3	652.0	857.4	1066.8	1244.4	1371.5

TEST NUMBER: P1009185

CATALOG NUMBER: S122DIP-B485D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	233.2	248.1	263.0	304.7	371.1	478.3	630.2	809.8	993.4	1162.1	1300.0
115°	256.0	269.4	282.8	325.5	386.0	482.3	615.3	772.1	935.8	1088.6	1218.6
117.5°	276.9	290.8	304.7	344.4	401.9	488.2	607.3	746.3	888.2	1025.1	1146.2
120°	297.7	311.6	325.5	364.2	417.8	494.2	600.4	726.4	854.4	977.5	1082.7
122.5°	318.6	333.0	347.3	383.1	431.7	501.1	596.4	709.5	827.6	937.8	1036.0
125°	338.4	352.3	366.2	401.9	446.6	508.1	591.5	693.7	801.8	904.1	991.4
127.5°	356.3	370.6	385.0	419.8	460.5	515.0	588.5	678.8	776.0	870.3	953.7
130°	373.1	387.0	400.9	435.7	473.4	523.0	586.5	663.9	751.2	836.6	915.0
132.5°	389.0	402.9	416.8	449.5	486.3	530.9	585.5	652.0	727.4	804.8	875.3
135°	402.9	416.8	430.7	462.4	497.2	536.9	584.5	641.1	705.6	771.1	836.6
137.5°	415.8	428.7	441.6	473.4	506.1	542.8	584.5	633.1	687.7	744.3	797.9
140°	426.7	439.6	452.5	482.3	513.1	546.8	583.5	626.2	670.8	718.5	764.1
142.5°	436.6	448.6	460.5	489.2	519.0	549.8	583.5	619.2	657.0	695.7	733.4
145°	447.6	458.5	469.4	496.2	524.0	551.8	581.5	613.3	644.1	676.8	707.6
147.5°	456.5	466.4	476.3	502.1	527.0	552.8	578.6	607.3	634.1	660.9	685.7
150°	465.4	474.4	483.3	506.1	528.9	551.8	575.6	599.4	623.2	645.0	665.9
152.5°	474.4	482.3	490.2	510.1	529.9	549.8	570.6	592.4	612.3	632.1	649.0
155°	482.3	489.8	497.2	514.1	530.9	547.8	564.7	583.5	602.4	618.2	633.1
157.5°	489.2	495.6	502.1	517.0	530.9	543.8	558.7	575.6	590.5	604.4	617.3
160°	496.2	501.6	507.1	519.0	530.9	540.8	552.8	566.6	579.5	590.5	601.4
162.5°	502.1	506.1	510.1	520.0	529.9	537.9	547.8	558.7	568.6	577.6	586.5
165°	506.1	509.1	512.1	521.0	527.9	533.9	540.8	549.8	557.7	564.7	571.6
167.5°	510.1	512.1	514.1	521.0	527.0	529.9	534.9	540.8	546.8	552.8	557.7
170°	512.1	513.6	515.0	520.0	525.0	527.0	529.9	533.9	538.9	541.8	545.8
172.5°	514.1	515.0	516.0	519.0	522.0	523.0	524.0	527.0	529.9	531.9	534.9
175°	515.0	515.5	516.0	518.0	520.0	519.0	520.0	521.0	524.0	525.0	526.0
177.5°	516.0	516.0	516.0	517.0	519.0	517.0	516.0	517.0	519.0	519.0	520.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P1009185

CATALOG NUMBER: S122DIP-B485D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	926.2	928.4	923.2	921.7	923.2	918.0	919.5	921.0	921.0	923.2	924.7
5°	872.4	869.4	864.2	862.7	861.2	863.5	862.0	864.2	864.9	870.2	870.9
7.5°	819.4	814.9	810.4	805.9	804.4	800.7	804.4	804.4	809.7	808.2	811.9
10°	756.6	755.9	749.9	747.7	744.7	738.7	746.9	744.7	748.4	755.1	756.6
12.5°	710.3	702.1	705.9	695.4	699.1	693.2	693.9	693.9	699.9	700.6	699.1
15°	666.3	659.5	649.8	645.4	643.1	640.1	649.8	650.6	646.1	656.6	652.8
17.5°	621.4	621.4	612.5	610.2	604.3	607.3	605.8	606.5	605.0	612.5	616.2
20°	582.6	578.9	575.9	576.6	569.2	567.7	566.2	567.7	572.9	578.1	579.6
22.5°	551.2	549.0	541.5	543.0	537.0	539.3	537.8	541.5	542.3	542.3	547.5
25°	521.4	518.4	519.1	516.1	513.9	513.9	511.6	513.9	516.9	518.4	519.1
27.5°	499.0	496.7	493.0	490.7	492.2	488.5	491.5	493.7	493.7	492.2	493.7
30°	472.1	473.6	473.6	466.1	469.1	467.6	469.8	471.3	471.3	472.1	470.6
32.5°	454.1	449.7	448.9	448.2	448.2	445.2	445.2	447.4	448.2	448.9	451.1
35°	430.2	430.2	426.5	428.7	425.8	426.5	425.8	426.5	428.0	425.8	428.0
37.5°	408.6	409.3	407.8	409.3	410.1	408.6	407.1	410.1	408.6	408.6	407.1
40°	389.9	389.2	389.9	389.9	389.9	390.6	389.2	389.2	389.2	387.7	386.2
42.5°	374.2	369.7	371.2	372.0	369.7	369.7	370.5	369.7	372.0	367.5	367.5
45°	351.8	350.3	351.1	351.1	352.6	350.3	351.8	352.6	350.3	349.6	348.1
47.5°	331.6	333.1	331.6	333.1	333.1	334.6	331.6	332.4	333.1	330.1	327.9
50°	311.5	311.5	313.7	313.0	313.7	312.2	312.2	311.5	312.2	310.7	308.5
52.5°	292.8	290.6	294.3	293.5	292.8	292.1	291.3	292.1	290.6	289.1	289.1
55°	269.6	269.6	271.9	272.6	272.6	271.1	269.6	270.4	269.6	268.9	268.1
57.5°	251.0	248.0	249.5	250.2	250.2	248.0	249.5	248.0	248.0	248.7	246.5
60°	227.1	227.1	225.6	227.8	227.8	226.3	226.3	227.1	225.6	224.8	224.1
62.5°	201.7	202.4	204.7	205.4	206.2	204.7	203.2	203.9	203.9	201.7	202.4
65°	180.0	181.5	184.5	183.7	182.3	183.0	181.5	182.3	180.0	180.8	178.5
67.5°	159.1	158.3	159.1	159.1	160.6	159.8	158.3	158.3	157.6	159.8	157.6
70°	136.7	136.7	136.7	136.7	137.4	138.2	136.7	135.2	135.9	134.4	133.7
72.5°	113.5	114.3	113.5	115.0	112.8	114.3	114.3	113.5	112.8	112.8	112.8
75°	91.9	93.4	91.1	91.9	91.1	92.6	91.9	91.9	90.4	89.6	90.4
77.5°	70.2	71.0	69.5	70.2	69.5	70.2	70.2	69.5	69.5	69.5	69.5
80°	50.0	50.8	50.0	49.3	48.6	50.0	48.6	49.3	50.0	49.3	50.8
82.5°	32.1	32.1	31.4	32.1	30.6	30.6	31.4	31.4	30.6	32.1	30.6
85°	15.7	15.7	17.2	15.7	14.9	14.9	14.9	15.7	14.9	16.4	15.7
87.5°	3.7	3.0	3.7	3.7	3.0	3.0	3.7	3.0	3.7	4.5	3.0
90°	32.2	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.2
92.5°	70.4	66.5	65.5	61.5	62.5	60.5	62.5	61.5	65.5	66.5	70.4
95°	146.9	136.0	123.1	115.1	112.1	113.1	112.1	115.1	123.1	136.0	146.9
97.5°	294.8	265.0	226.3	206.4	195.5	189.5	195.5	206.4	226.3	265.0	294.8
100°	587.0	527.0	444.6	401.9	373.1	355.3	373.1	401.9	444.6	527.0	587.0
102.5°	992.4	927.9	836.6	756.2	718.5	692.7	718.5	756.2	836.6	927.9	992.4
105°	1314.4	1298.0	1236.5	1175.0	1132.3	1118.4	1132.3	1175.0	1236.5	1298.0	1314.4
107.5°	1431.1	1450.9	1449.9	1440.9	1428.0	1405.2	1428.0	1440.9	1449.9	1450.9	1431.1
110°	1412.2	1452.8	1495.5	1514.4	1523.3	1522.3	1523.3	1514.4	1495.5	1452.8	1412.2

TEST NUMBER: P1009185

CATALOG NUMBER: S122DIP-B485D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1348.2	1396.3	1459.8	1494.5	1513.4	1520.3	1513.4	1494.5	1459.8	1396.3	1348.2
115°	1269.8	1320.9	1391.3	1437.0	1462.8	1471.7	1462.8	1437.0	1391.3	1320.9	1269.8
117.5°	1194.8	1243.4	1315.9	1364.5	1391.3	1398.3	1391.3	1364.5	1315.9	1243.4	1194.8
120°	1127.8	1173.0	1242.5	1289.1	1317.9	1327.8	1317.9	1289.1	1242.5	1173.0	1127.8
122.5°	1075.7	1115.4	1176.0	1221.6	1246.4	1254.4	1246.4	1221.6	1176.0	1115.4	1075.7
125°	1028.6	1065.8	1123.4	1161.1	1185.9	1193.8	1185.9	1161.1	1123.4	1065.8	1028.6
127.5°	988.4	1023.1	1073.8	1109.5	1131.3	1137.3	1131.3	1109.5	1073.8	1023.1	988.4
130°	947.8	980.5	1029.1	1062.8	1082.7	1090.6	1082.7	1062.8	1029.1	980.5	947.8
132.5°	905.6	935.8	983.4	1017.2	1035.0	1042.0	1035.0	1017.2	983.4	935.8	905.6
135°	864.4	892.1	934.8	967.6	985.4	989.4	985.4	967.6	934.8	892.1	864.4
137.5°	822.7	847.5	888.2	917.0	932.8	938.8	932.8	917.0	888.2	847.5	822.7
140°	786.0	807.8	839.5	865.4	880.2	886.2	880.2	865.4	839.5	807.8	786.0
142.5°	750.8	768.1	797.9	820.7	833.6	833.6	833.6	820.7	797.9	768.1	750.8
145°	722.0	736.3	760.2	777.0	787.0	789.9	787.0	777.0	760.2	736.3	722.0
147.5°	696.7	707.6	728.4	742.3	749.2	751.2	749.2	742.3	728.4	707.6	696.7
150°	674.8	683.7	698.6	710.5	716.5	717.5	716.5	710.5	698.6	683.7	674.8
152.5°	656.4	663.9	674.8	684.7	688.7	688.7	688.7	684.7	674.8	663.9	656.4
155°	638.6	644.1	655.0	661.9	665.9	663.9	665.9	661.9	655.0	644.1	638.6
157.5°	621.8	626.2	634.1	640.1	642.1	642.1	642.1	640.1	634.1	626.2	621.8
160°	604.8	608.3	615.3	620.2	621.2	621.2	621.2	620.2	615.3	608.3	604.8
162.5°	589.0	591.5	598.4	601.4	602.4	601.4	602.4	601.4	598.4	591.5	589.0
165°	573.6	575.6	579.5	583.5	583.5	582.5	583.5	583.5	579.5	575.6	573.6
167.5°	559.7	561.7	563.7	565.7	565.7	564.7	565.7	565.7	563.7	561.7	559.7
170°	546.8	547.8	548.8	551.8	550.8	548.8	550.8	551.8	548.8	547.8	546.8
172.5°	535.4	535.9	536.9	537.9	536.9	535.9	536.9	537.9	536.9	535.9	535.4
175°	526.5	527.0	527.0	527.9	527.0	525.0	527.0	527.9	527.0	527.0	526.5
177.5°	520.0	520.0	520.0	520.0	519.0	517.0	519.0	520.0	520.0	520.0	520.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P1009185

CATALOG NUMBER: S122DIP-B485D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	922.5	928.4	926.2	918.0	927.7	927.7	934.4	934.4	942.6	945.6	950.1
5°	870.2	874.7	878.4	874.7	881.4	891.8	897.8	903.0	914.2	918.7	925.5
7.5°	814.2	822.4	826.1	826.1	837.3	849.3	861.2	868.7	884.4	890.3	897.1
10°	759.6	769.3	776.8	776.1	794.7	802.2	817.1	834.3	850.0	859.0	868.7
12.5°	702.1	707.3	717.8	732.7	737.2	750.7	767.8	789.5	817.9	826.1	840.3
15°	654.3	668.5	676.7	683.4	693.9	706.6	725.3	746.2	774.6	792.5	807.4
17.5°	614.0	632.7	637.9	636.4	649.8	669.3	690.9	706.6	732.0	753.7	767.8
20°	581.1	588.6	597.5	601.3	611.7	632.7	653.6	671.5	692.4	709.6	726.0
22.5°	548.2	554.2	561.7	568.4	576.6	588.6	608.8	631.2	651.3	667.8	686.4
25°	521.4	525.1	531.8	537.0	546.0	554.2	568.4	593.1	617.0	626.7	643.1
27.5°	495.2	498.2	502.7	508.7	513.1	521.4	534.1	554.2	578.9	588.6	611.0
30°	472.1	474.3	478.8	481.8	484.0	493.7	503.4	519.1	537.8	551.2	567.7
32.5°	450.4	452.6	457.1	457.9	460.9	466.1	475.0	489.2	505.7	516.9	531.1
35°	426.5	428.0	432.5	434.0	436.2	440.7	447.4	457.9	472.8	481.0	493.7
37.5°	407.8	407.1	410.1	412.3	415.3	417.5	419.8	430.2	441.4	448.9	458.6
40°	387.7	386.2	386.9	389.9	391.4	394.4	394.4	404.8	412.3	418.3	425.8
42.5°	367.5	366.7	365.3	366.7	368.2	369.0	369.7	377.2	384.7	389.9	398.1
45°	347.3	346.6	345.1	345.8	345.8	347.3	349.6	352.6	357.8	362.3	366.7
47.5°	328.7	327.2	324.9	324.2	325.7	325.7	325.7	328.7	333.9	335.4	339.9
50°	309.2	307.0	304.0	302.5	302.5	301.8	303.3	304.0	308.5	310.0	313.7
52.5°	288.3	286.8	283.8	280.8	281.6	280.1	280.8	281.6	283.1	285.3	287.6
55°	267.4	264.4	262.2	261.4	259.2	259.2	256.9	259.9	259.2	259.9	262.9
57.5°	247.2	244.2	240.5	239.0	236.8	236.0	234.5	233.8	234.5	236.8	239.0
60°	223.3	221.8	219.6	217.4	215.9	213.6	212.1	212.1	211.4	211.4	212.1
62.5°	200.2	199.4	196.4	195.7	194.2	192.7	190.5	189.0	189.0	190.5	191.2
65°	177.8	177.0	174.8	174.0	170.3	168.8	168.1	167.3	165.8	165.8	165.8
67.5°	156.9	154.6	154.6	150.9	147.9	146.4	144.9	144.2	144.2	144.2	144.9
70°	133.7	133.7	131.5	129.2	126.2	127.0	124.7	122.5	122.5	121.0	121.8
72.5°	111.3	110.5	108.3	107.6	105.3	103.1	101.6	103.1	100.8	100.1	100.8
75°	89.6	88.9	87.4	85.9	86.6	84.4	82.2	81.4	81.4	79.9	79.9
77.5°	68.7	70.2	67.2	66.5	65.0	63.5	62.7	62.0	62.0	62.0	63.5
80°	47.8	48.6	48.6	47.1	47.8	45.6	45.6	45.6	43.3	44.1	44.8
82.5°	30.6	30.6	29.9	30.6	29.9	29.9	29.1	29.1	28.4	28.4	29.1
85°	17.2	16.4	15.7	17.2	16.4	16.4	15.7	15.7	15.7	15.7	15.7
87.5°	3.7	4.5	4.5	4.5	4.5	5.2	5.2	5.2	6.0	6.0	6.0
90°	31.8	29.8	31.8	32.7	33.7	32.7	26.8	19.8	14.9	13.4	11.9
92.5°	74.4	85.3	100.2	128.0	152.8	150.8	117.1	79.4	52.6	47.2	41.7
95°	157.8	199.5	260.0	340.4	389.0	344.4	229.2	142.9	97.3	85.4	73.4
97.5°	324.5	424.7	531.9	639.1	634.1	490.2	304.7	184.6	126.0	112.6	99.2
100°	647.0	783.0	906.0	926.9	784.0	539.9	325.5	204.4	151.8	137.9	124.0
102.5°	1056.9	1147.2	1151.2	1034.1	788.9	521.0	326.5	222.3	174.7	160.8	146.9
105°	1330.8	1317.9	1205.7	999.3	735.4	495.2	331.5	243.1	196.5	182.6	168.7
107.5°	1411.2	1313.9	1147.2	925.9	685.7	481.3	342.4	264.0	218.3	204.4	190.5
110°	1371.5	1244.4	1066.8	857.4	652.0	477.3	356.3	284.8	241.1	226.8	212.4

TEST NUMBER: P1009185

CATALOG NUMBER: S122DIP-B485D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1300.0	1162.1	993.4	809.8	630.2	478.3	371.1	304.7	263.0	248.1	233.2
115°	1218.6	1088.6	935.8	772.1	615.3	482.3	386.0	325.5	282.8	269.4	256.0
117.5°	1146.2	1025.1	888.2	746.3	607.3	488.2	401.9	344.4	304.7	290.8	276.9
120°	1082.7	977.5	854.4	726.4	600.4	494.2	417.8	364.2	325.5	311.6	297.7
122.5°	1036.0	937.8	827.6	709.5	596.4	501.1	431.7	383.1	347.3	333.0	318.6
125°	991.4	904.1	801.8	693.7	591.5	508.1	446.6	401.9	366.2	352.3	338.4
127.5°	953.7	870.3	776.0	678.8	588.5	515.0	460.5	419.8	385.0	370.6	356.3
130°	915.0	836.6	751.2	663.9	586.5	523.0	473.4	435.7	400.9	387.0	373.1
132.5°	875.3	804.8	727.4	652.0	585.5	530.9	486.3	449.5	416.8	402.9	389.0
135°	836.6	771.1	705.6	641.1	584.5	536.9	497.2	462.4	430.7	416.8	402.9
137.5°	797.9	744.3	687.7	633.1	584.5	542.8	506.1	473.4	441.6	428.7	415.8
140°	764.1	718.5	670.8	626.2	583.5	546.8	513.1	482.3	452.5	439.6	426.7
142.5°	733.4	695.7	657.0	619.2	583.5	549.8	519.0	489.2	460.5	448.6	436.6
145°	707.6	676.8	644.1	613.3	581.5	551.8	524.0	496.2	469.4	458.5	447.6
147.5°	685.7	660.9	634.1	607.3	578.6	552.8	527.0	502.1	476.3	466.4	456.5
150°	665.9	645.0	623.2	599.4	575.6	551.8	528.9	506.1	483.3	474.4	465.4
152.5°	649.0	632.1	612.3	592.4	570.6	549.8	529.9	510.1	490.2	482.3	474.4
155°	633.1	618.2	602.4	583.5	564.7	547.8	530.9	514.1	497.2	489.8	482.3
157.5°	617.3	604.4	590.5	575.6	558.7	543.8	530.9	517.0	502.1	495.6	489.2
160°	601.4	590.5	579.5	566.6	552.8	540.8	530.9	519.0	507.1	501.6	496.2
162.5°	586.5	577.6	568.6	558.7	547.8	537.9	529.9	520.0	510.1	506.1	502.1
165°	571.6	564.7	557.7	549.8	540.8	533.9	527.9	521.0	512.1	509.1	506.1
167.5°	557.7	552.8	546.8	540.8	534.9	529.9	527.0	521.0	514.1	512.1	510.1
170°	545.8	541.8	538.9	533.9	529.9	527.0	525.0	520.0	515.0	513.6	512.1
172.5°	534.9	531.9	529.9	527.0	524.0	523.0	522.0	519.0	516.0	515.0	514.1
175°	526.0	525.0	524.0	521.0	520.0	519.0	520.0	518.0	516.0	515.5	515.0
177.5°	520.0	519.0	519.0	517.0	516.0	517.0	519.0	517.0	516.0	516.0	516.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P1009185

CATALOG NUMBER: S122DIP-B485D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	971.8	971.8	971.8	971.8
2.5°	953.8	953.8	965.0	977.0
5°	932.9	938.1	956.1	972.5
7.5°	912.8	921.7	944.1	965.0
10°	888.1	900.1	927.7	952.3
12.5°	864.2	875.4	907.5	935.2
15°	830.6	844.8	879.1	913.5
17.5°	797.0	811.2	853.0	893.3
20°	757.4	776.1	823.1	876.9
22.5°	720.8	743.9	796.2	839.6
25°	680.5	716.3	764.9	820.9
27.5°	644.6	680.5	729.8	786.5
30°	604.3	640.9	691.7	743.9
32.5°	565.4	599.0	648.3	712.6
35°	525.1	557.2	605.0	670.0
37.5°	488.5	519.9	572.2	631.9
40°	452.6	485.5	530.3	590.1
42.5°	419.0	448.2	488.5	548.2
45°	388.4	409.3	446.7	502.7
47.5°	356.3	375.0	409.3	465.3
50°	326.4	342.1	372.0	424.3
52.5°	297.3	310.7	338.4	380.2
55°	271.1	283.8	304.0	345.1
57.5°	244.2	254.0	273.4	306.2
60°	218.1	227.1	242.8	269.6
62.5°	192.0	199.4	214.4	236.0
65°	168.8	174.8	186.0	204.7
67.5°	146.4	150.1	159.1	174.0
70°	124.7	127.7	135.2	147.1
72.5°	101.6	104.6	112.8	121.0
75°	82.2	82.9	88.9	95.6
77.5°	64.2	63.5	68.0	73.2
80°	44.1	46.3	50.0	52.3
82.5°	29.9	30.6	32.1	33.6
85°	16.4	17.2	17.2	19.4
87.5°	6.7	7.5	7.5	8.2
90°	9.9	7.9	4.0	1.0
92.5°	33.7	28.8	20.8	14.9
95°	57.6	48.6	38.7	34.7
97.5°	81.4	68.5	57.6	51.6
100°	104.2	88.3	79.4	76.4
102.5°	126.0	110.2	101.2	99.2
105°	146.9	132.0	125.0	121.1
107.5°	168.7	154.8	147.9	144.9
110°	191.5	178.6	172.7	168.7



TEST NUMBER: P1009185

CATALOG NUMBER: S122DIP-B485D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	213.4	201.5	194.5	190.5
115°	236.2	224.3	218.3	213.4
117.5°	258.0	247.1	241.1	237.2
120°	277.9	268.9	263.0	259.0
122.5°	298.7	288.8	282.8	279.8
125°	318.6	306.6	300.7	297.7
127.5°	337.4	324.5	316.6	312.6
130°	353.3	339.4	329.5	325.5
132.5°	368.2	353.3	342.4	337.4
135°	380.1	365.2	353.3	349.3
137.5°	393.0	377.1	365.2	360.2
140°	404.9	389.0	377.1	373.1
142.5°	415.8	399.9	389.0	386.0
145°	427.7	412.8	402.9	398.9
147.5°	439.6	425.7	415.8	412.8
150°	450.5	437.6	429.7	426.7
152.5°	460.5	449.5	441.6	440.6
155°	471.4	460.5	454.5	453.5
157.5°	480.3	470.4	465.4	464.4
160°	488.2	480.3	476.3	475.3
162.5°	495.2	489.2	485.3	486.3
165°	501.1	495.2	493.2	494.2
167.5°	506.1	502.1	500.2	501.1
170°	510.1	507.1	506.1	508.1
172.5°	513.1	510.1	511.1	512.1
175°	515.0	513.1	514.1	515.0
177.5°	516.0	514.1	515.0	517.0
180°	516.0	516.0	516.0	516.0

(END OF REPORT)