

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009221

Luminaire Tested: S122DIP-B675D1080UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009221
REPORT IS A COMBINATION OF REPORTS P984444 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D1080UB30-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7154.0 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009221

CATALOG NUMBER: S122DIP-B675D1080UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1009221

CATALOG NUMBER: S122DIP-B675D1080UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41
2	88	81	75	70	80	74	69	65	61	58	55	49	47	45	38	37	35
3	80	71	64	59	73	65	59	55	54	50	46	44	41	38	34	32	31
4	74	63	56	50	67	58	52	47	48	44	40	39	36	33	31	29	27
5	68	57	49	43	62	52	45	40	44	38	35	36	32	29	28	26	24
6	63	51	43	38	57	47	40	35	39	34	30	32	28	26	26	23	21
7	58	46	38	33	53	42	36	31	36	31	27	29	26	23	23	21	19
8	54	42	34	29	49	39	32	27	33	28	24	27	23	20	22	19	17
9	50	38	31	26	46	35	29	25	30	25	21	25	21	18	20	17	15
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21137	21137	21137	21137
5°	21187	22537	21268	17929
10°	20941	24603	21073	14781
15°	20433	25949	20718	12452
20°	20114	24365	20114	10822
25°	19473	20932	19562	9678
30°	18418	16454	18769	8766
35°	17484	11378	17776	8020
40°	16410	8590	16596	7427
45°	15085	7060	15332	6785
50°	13942	6196	13965	6211
55°	12636	5279	12716	5588
60°	11243	4410	11397	4877
65°	9996	3587	10178	4165
70°	8757	2815	8978	3359
75°	7351	2042	7636	2437
80°	5732	1295	6148	1446
85°	3772	651	4054	482

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 21850 cd/sqm

TEST NUMBER: P1009221

CATALOG NUMBER: S122DIP-B675D1080UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.2	1.8
10°-20°	370.2	5.2
20°-30°	537.2	7.5
30°-40°	566.3	7.9
40°-50°	501.2	7.0
50°-60°	400.2	5.6
60°-70°	271.8	3.8
70°-80°	139.1	1.9
80°-90°	36.7	0.5
90°-100°	235.3	3.3
100°-110°	828.8	11.6
110°-120°	870.4	12.2
120°-130°	716.1	10.0
130°-140°	575.3	8.0
140°-150°	434.5	6.1
150°-160°	305.5	4.3
160°-170°	179.8	2.5
170°-180°	58.5	0.8
0°-30°	1034.6	14.5
0°-40°	1600.9	22.4
0°-60°	2502.3	35.0
0°-90°	2949.9	41.2
90°-120°	1934.5	27.0
90°-150°	3660.3	51.2
90°-180°	4204.0	58.8
0°-180°	7154.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1335	1335	1335	1335	1335	
5°	1336	1491	1341	1186	1336	127
15°	1255	1833	1273	880	1255	355
25°	1128	1527	1133	706	1128	516
35°	921	831	936	586	921	576
45°	691	501	702	481	691	536
55°	474	352	477	373	474	423
65°	281	217	286	252	281	280
75°	131	107	136	127	131	141
85°	27	28	29	20	27	31
90°	1	38	1	38	1	4
95°	41	132	41	132	41	42
105°	142	1308	142	1308	142	150
115°	250	1722	250	1722	250	248
125°	348	1397	348	1397	348	310
135°	409	1158	409	1158	409	316
145°	467	924	467	924	467	293
155°	531	777	531	777	531	244
165°	578	682	578	682	578	163
175°	602	614	602	614	602	57
180°	604	604	604	604	604	

TEST NUMBER: P1009221

CATALOG NUMBER: S122DIP-B675D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1342.4	1345.5	1350.7	1351.7	1361.9	1370.2	1379.4	1379.4	1382.5	1381.4	1373.2
5°	1336.3	1345.5	1358.9	1370.2	1388.6	1396.8	1409.2	1418.4	1426.6	1432.8	1431.7
7.5°	1326.0	1342.4	1361.9	1383.5	1408.1	1422.5	1440.0	1456.4	1467.7	1477.9	1485.1
10°	1308.6	1336.3	1363.0	1391.7	1423.5	1443.0	1463.6	1485.1	1502.6	1522.1	1540.5
12.5°	1285.0	1325.0	1357.8	1395.8	1434.8	1456.4	1489.2	1505.6	1539.5	1588.8	1602.1
15°	1255.2	1309.6	1340.4	1388.6	1440.0	1457.4	1502.6	1529.2	1599.0	1629.8	1666.8
17.5°	1227.5	1288.1	1329.1	1384.5	1434.8	1468.7	1512.8	1567.2	1625.7	1669.9	1710.9
20°	1204.9	1263.4	1312.7	1374.3	1437.9	1481.0	1527.2	1592.9	1656.5	1701.7	1733.5
22.5°	1153.6	1228.5	1286.0	1354.8	1431.7	1491.3	1535.4	1607.2	1676.0	1703.7	1731.4
25°	1127.9	1192.6	1259.3	1337.3	1427.6	1498.5	1536.4	1616.5	1677.0	1687.3	1693.5
27.5°	1080.7	1153.6	1231.6	1320.9	1426.6	1486.1	1534.4	1607.2	1655.5	1648.3	1629.8
30°	1022.2	1111.5	1197.7	1294.2	1412.2	1476.9	1522.1	1588.8	1613.4	1576.5	1543.6
32.5°	979.1	1063.3	1158.7	1270.6	1395.8	1457.4	1501.5	1553.9	1559.0	1492.3	1436.9
35°	920.6	1014.0	1121.8	1239.8	1368.1	1423.5	1464.6	1496.4	1471.8	1378.4	1312.7
37.5°	868.3	960.7	1075.6	1195.7	1330.1	1384.5	1417.4	1422.5	1361.9	1279.8	1183.4
40°	810.8	906.3	1026.3	1152.6	1288.1	1335.3	1355.8	1340.4	1253.2	1157.7	1045.8
42.5°	753.3	847.8	977.1	1106.4	1234.7	1274.7	1282.9	1240.8	1134.1	1022.2	892.9
45°	690.7	789.3	918.6	1048.9	1173.1	1195.7	1196.7	1136.2	1009.9	892.9	772.8
47.5°	639.4	730.8	859.0	989.4	1094.1	1109.5	1103.3	1033.5	896.0	764.6	659.9
50°	583.0	670.2	797.5	925.8	1015.0	1019.2	1003.8	904.2	769.8	649.7	566.5
52.5°	522.4	610.7	727.7	850.8	930.9	924.7	895.0	788.2	662.0	562.4	498.8
55°	474.2	552.2	662.0	782.1	838.5	821.1	788.2	679.4	579.9	495.7	440.3
57.5°	420.8	489.6	597.3	702.0	734.9	718.4	685.6	584.0	491.6	428.0	391.0
60°	370.5	433.1	527.5	614.8	640.4	623.0	585.0	493.7	427.0	373.6	345.9
62.5°	324.3	378.7	457.7	537.8	548.1	530.6	497.8	423.9	366.4	324.3	303.8
65°	281.2	332.5	396.2	456.7	466.0	447.5	413.6	360.2	312.0	285.3	265.8
67.5°	239.1	280.2	336.6	380.8	385.9	368.5	340.7	297.6	267.9	239.1	224.8
70°	202.2	233.0	277.1	313.0	315.1	298.7	284.3	245.3	222.7	202.2	190.9
72.5°	166.3	187.8	221.7	248.4	249.4	239.1	225.8	201.2	181.7	167.3	156.0
75°	131.4	149.8	170.4	194.0	193.0	184.7	174.5	159.1	142.7	133.4	128.3
77.5°	100.6	111.9	128.3	143.7	143.7	139.6	133.4	122.1	111.9	102.6	97.5
80°	71.8	79.0	92.4	97.5	99.6	98.5	93.4	85.2	81.1	73.9	71.8
82.5°	46.2	51.3	57.5	62.6	65.7	63.6	62.6	58.5	52.3	50.3	48.2
85°	26.7	28.7	31.8	34.9	35.9	34.9	36.9	33.9	30.8	30.8	29.8
87.5°	11.3	12.3	14.4	14.4	15.4	15.4	14.4	15.4	15.4	14.4	13.3
90°	1.2	4.6	9.3	11.6	13.9	15.6	17.4	23.2	31.3	38.3	39.5
92.5°	17.4	24.4	33.7	39.5	48.8	55.2	61.5	92.9	137.0	176.5	178.8
95°	40.6	45.3	56.9	67.3	85.9	99.8	113.8	167.2	268.2	402.8	455.1
97.5°	60.4	67.3	80.1	95.2	116.1	131.8	147.4	215.9	356.4	573.5	741.8
100°	89.4	92.9	103.3	121.9	145.1	161.4	177.6	239.2	380.8	631.6	917.1
102.5°	116.1	118.4	128.9	147.4	171.8	188.0	204.3	260.1	382.0	609.5	923.0
105°	141.6	146.3	154.4	171.8	197.4	213.6	229.9	284.4	387.8	579.3	860.3
107.5°	169.5	173.0	181.1	197.4	222.9	239.2	255.4	308.8	400.5	563.1	802.2
110°	197.4	202.0	209.0	224.1	248.4	265.2	282.1	333.2	416.8	558.4	762.7

TEST NUMBER: P1009221

CATALOG NUMBER: S122DIP-B675D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	222.9	227.5	235.7	249.6	272.8	290.2	307.7	356.4	434.2	559.6	737.2
115°	249.6	255.4	262.4	276.3	299.5	315.2	330.9	380.8	451.6	564.2	719.8
117.5°	277.5	282.1	289.1	301.8	323.9	340.2	356.4	402.8	470.2	571.2	710.5
120°	303.0	307.7	314.6	325.1	348.3	364.6	380.8	426.1	488.8	578.2	702.4
122.5°	327.4	330.9	337.8	349.4	372.7	389.5	406.3	448.1	505.0	586.3	697.7
125°	348.3	351.8	358.7	372.7	395.9	412.2	428.4	470.2	522.4	594.4	691.9
127.5°	365.7	370.3	379.6	394.7	416.8	433.6	450.4	491.1	538.7	602.5	688.4
130°	380.8	385.4	397.0	413.3	436.5	452.8	469.0	509.7	553.8	611.8	686.1
132.5°	394.7	400.5	413.3	430.7	455.1	471.4	487.6	525.9	568.9	621.1	685.0
135°	408.7	413.3	427.2	444.6	471.3	487.6	503.8	541.0	581.6	628.1	683.8
137.5°	421.4	427.2	441.2	459.7	486.4	501.5	516.6	553.8	592.1	635.0	683.8
140°	436.5	441.2	455.1	473.7	499.2	514.3	529.4	564.2	600.2	639.7	682.6
142.5°	451.6	455.1	467.9	486.4	510.8	524.8	538.7	572.3	607.2	643.2	682.6
145°	466.7	471.3	483.0	500.4	523.6	536.4	549.1	580.5	613.0	645.5	680.3
147.5°	483.0	486.4	498.0	514.3	534.0	545.6	557.3	587.4	616.5	646.6	676.8
150°	499.2	502.7	512.0	527.1	544.5	555.0	565.4	592.1	618.8	645.5	673.3
152.5°	515.5	516.6	525.9	538.7	554.9	564.2	573.5	596.7	619.9	643.2	667.5
155°	530.6	531.7	538.7	551.4	564.2	572.9	581.6	601.4	621.1	640.8	660.6
157.5°	543.3	544.5	550.3	561.9	572.3	579.8	587.4	604.9	621.1	636.2	653.6
160°	556.1	557.3	561.9	571.2	580.5	586.8	593.2	607.2	621.1	632.7	646.6
162.5°	568.9	567.7	572.3	579.3	587.4	592.0	596.7	608.3	619.9	629.2	640.8
165°	578.2	577.0	579.3	586.3	592.1	595.6	599.0	609.5	617.6	624.6	632.7
167.5°	586.3	585.1	587.4	592.1	596.7	599.0	601.4	609.5	616.5	619.9	625.7
170°	594.4	592.1	593.2	596.7	599.0	600.8	602.5	608.3	614.1	616.5	619.9
172.5°	599.0	597.9	596.7	600.2	601.4	602.6	603.7	607.2	610.7	611.8	613.0
175°	602.5	601.4	600.2	602.5	602.5	603.1	603.7	606.0	608.3	607.2	608.3
177.5°	604.9	602.5	601.4	603.7	603.7	603.7	603.7	604.9	607.2	604.9	603.7
180°	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7

TEST NUMBER: P1009221

CATALOG NUMBER: S122DIP-B675D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1387.6	1388.6	1390.7	1400.9	1406.1	1407.1	1403.0	1412.2	1415.3	1412.2	1410.2
5°	1453.3	1459.5	1471.8	1485.1	1484.1	1485.1	1491.3	1497.4	1499.5	1491.3	1494.3
7.5°	1510.8	1523.1	1536.4	1557.0	1557.0	1567.2	1571.3	1576.5	1588.8	1582.6	1580.6
10°	1576.5	1592.9	1617.5	1650.3	1651.4	1661.6	1671.9	1688.3	1693.5	1689.4	1691.4
12.5°	1658.6	1690.4	1692.4	1728.4	1744.8	1746.8	1763.2	1760.2	1770.4	1770.4	1787.9
15°	1694.5	1743.7	1771.5	1806.4	1816.6	1804.3	1817.6	1832.0	1833.0	1833.0	1832.0
17.5°	1759.1	1778.6	1806.4	1824.8	1828.9	1828.9	1830.0	1836.1	1832.0	1823.8	1830.0
20°	1772.5	1780.7	1791.0	1788.9	1791.0	1780.7	1770.4	1760.2	1761.2	1756.1	1771.5
22.5°	1747.9	1745.8	1722.2	1706.8	1706.8	1686.3	1666.8	1657.5	1648.3	1651.4	1656.5
25°	1686.3	1654.5	1625.7	1603.1	1598.0	1565.2	1538.5	1530.3	1514.9	1527.2	1529.2
27.5°	1587.7	1551.8	1505.6	1486.1	1459.5	1446.1	1427.6	1403.0	1371.2	1389.7	1386.6
30°	1482.0	1428.7	1390.7	1343.5	1301.4	1298.3	1263.4	1222.4	1205.9	1205.9	1215.2
32.5°	1364.0	1293.2	1237.8	1171.1	1130.0	1112.5	1070.5	1029.4	1038.7	1007.9	1019.2
35°	1226.5	1133.1	1063.3	998.6	967.8	947.3	892.9	870.3	845.7	831.3	858.0
37.5°	1095.1	987.3	898.0	827.2	815.9	779.0	742.0	727.7	713.3	719.5	718.4
40°	935.0	839.5	759.5	704.1	684.6	667.1	642.5	625.0	615.8	620.9	622.0
42.5°	790.3	710.2	650.7	611.7	595.3	583.0	570.6	556.3	553.2	553.2	557.3
45°	678.4	612.7	572.7	540.9	531.6	522.4	513.2	507.0	505.0	500.9	503.9
47.5°	589.1	536.8	512.1	488.5	478.3	476.2	468.0	464.9	460.8	459.8	460.8
50°	514.2	481.4	458.8	445.4	438.2	435.2	431.1	424.9	422.9	428.0	425.9
52.5°	461.9	431.1	418.7	405.4	401.3	397.2	391.0	392.1	391.0	389.0	389.0
55°	409.5	390.0	377.7	367.4	366.4	362.3	357.2	355.1	354.1	352.0	355.1
57.5°	367.4	352.0	340.7	331.5	327.4	327.4	322.3	318.2	318.2	317.1	318.2
60°	325.3	310.0	302.8	293.5	290.5	289.4	286.3	284.3	281.2	281.2	281.2
62.5°	286.3	274.0	265.8	257.6	258.6	253.5	249.4	247.3	247.3	248.4	248.4
65°	249.4	241.2	230.9	223.7	221.7	220.7	218.6	217.6	214.5	216.6	216.6
67.5°	215.5	204.2	198.1	195.0	191.9	190.9	188.8	186.8	185.8	184.7	186.8
70°	181.7	172.4	167.3	165.2	162.2	161.1	160.1	157.0	158.1	159.1	160.1
72.5°	150.9	142.7	141.6	135.5	135.5	135.5	131.4	133.4	132.4	130.3	132.4
75°	119.1	114.9	112.9	109.8	110.8	109.8	108.8	105.7	105.7	106.7	107.8
77.5°	94.4	90.3	89.3	86.2	84.2	86.2	84.2	83.1	83.1	84.2	84.2
80°	69.8	67.7	64.7	64.7	64.7	63.6	63.6	63.6	62.6	61.6	62.6
82.5°	46.2	46.2	45.2	44.1	45.2	43.1	44.1	44.1	44.1	44.1	44.1
85°	29.8	28.7	28.7	27.7	27.7	27.7	28.7	26.7	26.7	27.7	27.7
87.5°	13.3	13.3	13.3	14.4	13.3	13.3	13.3	14.4	13.3	13.3	13.3
90°	38.3	37.2	34.8	37.2	37.8	38.3	38.3	38.3	38.3	38.3	38.3
92.5°	149.8	117.3	99.8	87.1	82.4	77.8	76.6	72.0	73.1	70.8	73.1
95°	398.2	304.2	233.3	184.6	171.8	159.0	144.0	134.7	131.2	132.3	131.2
97.5°	747.6	622.3	496.9	379.6	344.8	310.0	264.7	241.5	228.7	221.7	228.7
100°	1084.3	1059.9	916.0	756.9	686.7	616.5	520.1	470.2	436.5	415.6	436.5
102.5°	1209.7	1346.7	1342.1	1236.4	1161.0	1085.5	978.7	884.6	840.5	810.3	840.5
105°	1169.1	1410.5	1541.7	1556.8	1537.6	1518.5	1446.5	1374.6	1324.6	1308.4	1324.6
107.5°	1083.2	1342.1	1537.1	1650.9	1674.1	1697.3	1696.1	1685.7	1670.6	1643.9	1670.6
110°	1003.1	1248.0	1455.8	1604.4	1652.0	1699.6	1749.5	1771.6	1782.0	1780.9	1782.0

TEST NUMBER: P1009221

CATALOG NUMBER: S122DIP-B675D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	947.3	1162.1	1359.5	1520.8	1577.1	1633.4	1707.7	1748.4	1770.4	1778.6	1770.4
115°	903.2	1094.8	1273.6	1425.6	1485.4	1545.2	1627.6	1681.0	1711.2	1721.7	1711.2
117.5°	873.0	1039.0	1199.3	1340.9	1397.8	1454.7	1539.4	1596.3	1627.6	1635.8	1627.6
120°	849.8	999.6	1143.5	1266.6	1319.4	1372.2	1453.5	1508.1	1541.7	1553.3	1541.7
122.5°	830.1	968.2	1097.1	1212.0	1258.4	1304.9	1375.7	1429.1	1458.1	1467.4	1458.1
125°	811.5	938.0	1057.6	1159.8	1203.4	1246.9	1314.2	1358.3	1387.3	1396.6	1387.3
127.5°	794.1	907.9	1018.1	1115.7	1156.3	1196.9	1256.1	1297.9	1323.5	1330.4	1323.5
130°	776.7	878.8	978.7	1070.4	1108.7	1147.0	1203.9	1243.4	1266.6	1275.9	1266.6
132.5°	762.7	851.0	941.5	1024.0	1059.4	1094.8	1150.5	1190.0	1210.9	1219.0	1210.9
135°	750.0	825.4	902.1	978.7	1011.2	1043.7	1093.6	1131.9	1152.8	1157.5	1152.8
137.5°	740.7	804.5	870.7	933.4	962.4	991.4	1039.0	1072.7	1091.3	1098.3	1091.3
140°	732.6	784.8	840.5	893.9	919.4	945.0	982.2	1012.3	1029.8	1036.7	1029.8
142.5°	724.4	768.5	813.8	857.9	878.2	898.6	933.4	960.1	975.2	975.2	975.2
145°	717.5	753.5	791.8	827.8	844.6	861.4	889.3	909.0	920.6	924.1	920.6
147.5°	710.5	741.8	773.2	802.2	815.0	827.8	852.1	868.4	876.5	878.8	876.5
150°	701.2	729.1	754.6	779.0	789.4	799.9	817.3	831.2	838.2	839.4	838.2
152.5°	693.1	716.3	739.5	759.3	768.0	776.7	789.4	801.1	805.7	805.7	805.7
155°	682.6	704.7	723.3	740.7	747.1	753.5	766.2	774.3	779.0	776.7	779.0
157.5°	673.3	690.8	707.0	722.1	727.4	732.6	741.8	748.8	751.1	751.1	751.1
160°	662.9	678.0	690.8	703.5	707.6	711.7	719.8	725.6	726.8	726.8	726.8
162.5°	653.6	665.2	675.7	686.1	689.0	691.9	700.0	703.5	704.7	703.5	704.7
165°	643.2	652.5	660.6	668.7	671.0	673.3	678.0	682.6	682.6	681.5	682.6
167.5°	632.7	639.7	646.6	652.5	654.8	657.1	659.4	661.7	661.7	660.6	661.7
170°	624.6	630.4	633.9	638.5	639.6	640.8	642.0	645.5	644.3	642.0	644.3
172.5°	616.5	619.9	622.3	625.7	626.3	626.9	628.1	629.2	628.1	626.9	628.1
175°	609.5	613.0	614.1	615.3	615.9	616.5	616.5	617.6	616.5	614.1	616.5
177.5°	604.9	607.2	607.2	608.3	608.3	608.3	608.3	608.3	607.2	604.9	607.2
180°	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7

TEST NUMBER: P1009221

CATALOG NUMBER: S122DIP-B675D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1415.3	1408.1	1402.0	1403.0	1408.1	1404.0	1393.8	1380.4	1375.3	1369.1	1375.3
5°	1500.5	1494.3	1482.0	1483.1	1480.0	1475.9	1459.5	1438.9	1438.9	1422.5	1420.5
7.5°	1584.7	1575.4	1567.2	1565.2	1553.9	1545.7	1531.3	1502.6	1491.3	1471.8	1460.5
10°	1679.1	1671.9	1662.7	1651.4	1645.2	1630.8	1607.2	1565.2	1544.6	1518.0	1498.5
12.5°	1774.5	1773.5	1753.0	1730.4	1729.4	1706.8	1690.4	1633.9	1606.2	1570.3	1524.1
15°	1835.1	1830.0	1818.7	1807.4	1810.5	1785.8	1748.9	1682.2	1663.7	1620.6	1571.3
17.5°	1834.1	1834.1	1831.0	1828.9	1825.9	1818.7	1798.1	1754.0	1724.2	1669.9	1623.7
20°	1775.6	1788.9	1792.0	1791.0	1801.2	1806.4	1805.3	1777.6	1754.0	1705.8	1658.6
22.5°	1658.6	1689.4	1702.7	1710.9	1732.5	1743.7	1770.4	1760.2	1754.0	1718.1	1678.1
25°	1549.8	1560.0	1600.1	1602.1	1631.9	1659.6	1686.3	1703.7	1726.3	1713.0	1679.1
27.5°	1409.2	1432.8	1461.5	1483.1	1489.2	1545.7	1589.8	1622.6	1674.0	1678.1	1666.8
30°	1250.1	1261.4	1308.6	1337.3	1370.2	1411.2	1474.8	1531.3	1577.5	1619.6	1633.9
32.5°	1056.1	1102.3	1130.0	1164.9	1193.6	1266.5	1344.5	1417.4	1470.7	1541.6	1572.3
35°	878.5	914.5	961.7	976.0	1028.4	1090.0	1191.6	1285.0	1366.1	1437.9	1500.5
37.5°	731.8	760.5	810.8	833.4	864.2	943.2	1028.4	1144.4	1241.9	1330.1	1408.1
40°	631.2	652.8	690.7	697.9	723.6	795.4	864.2	973.0	1102.3	1221.3	1306.5
42.5°	562.4	572.7	598.4	607.6	624.0	672.3	733.8	836.5	956.5	1079.7	1199.8
45°	513.2	520.4	535.7	544.0	564.5	586.0	636.3	718.4	812.9	937.0	1066.4
47.5°	469.0	478.3	484.4	489.6	500.9	524.5	557.3	617.9	708.2	822.1	947.3
50°	432.1	435.2	446.5	447.5	454.7	470.1	500.9	537.8	609.6	702.0	823.1
52.5°	395.1	398.2	405.4	412.6	415.7	428.0	448.5	479.3	532.7	605.5	713.3
55°	358.2	362.3	369.5	374.6	377.7	388.0	400.3	430.0	472.1	523.4	611.7
57.5°	321.2	330.5	332.5	335.6	340.7	352.0	363.3	380.8	413.6	460.8	525.5
60°	286.3	289.4	296.6	299.7	304.8	311.0	325.3	338.7	362.3	399.2	457.7
62.5°	250.4	257.6	260.7	263.8	267.9	275.1	284.3	298.7	319.2	349.0	395.1
65°	219.6	220.7	226.8	230.9	235.0	240.2	249.4	262.7	275.1	302.8	336.6
67.5°	189.9	191.9	194.0	198.1	203.2	208.3	216.6	223.7	239.1	257.6	284.3
70°	161.1	161.1	166.3	169.3	168.3	174.5	180.6	188.8	200.1	217.6	239.1
72.5°	135.5	134.5	138.6	139.6	141.6	145.7	149.8	158.1	164.2	177.6	194.0
75°	107.8	109.8	111.9	111.9	114.9	118.0	122.1	126.2	133.4	141.6	154.0
77.5°	85.2	85.2	87.2	88.3	91.3	90.3	94.4	98.5	103.7	110.8	120.1
80°	62.6	64.7	64.7	64.7	65.7	66.7	70.8	73.9	77.0	82.1	86.2
82.5°	44.1	44.1	46.2	46.2	46.2	48.2	48.2	49.3	51.3	54.4	57.5
85°	27.7	27.7	27.7	28.7	27.7	28.7	30.8	29.8	30.8	32.8	32.8
87.5°	13.3	13.3	13.3	13.3	13.3	14.4	13.3	14.4	15.4	15.4	15.4
90°	38.3	38.3	38.3	37.8	37.2	34.8	37.2	38.3	39.5	38.3	31.3
92.5°	72.0	76.6	77.8	82.4	87.1	99.8	117.3	149.8	178.8	176.5	137.0
95°	134.7	144.0	159.0	171.8	184.6	233.3	304.2	398.2	455.1	402.8	268.2
97.5°	241.5	264.7	310.0	344.8	379.6	496.9	622.3	747.6	741.8	573.5	356.4
100°	470.2	520.1	616.5	686.7	756.9	916.0	1059.9	1084.3	917.1	631.6	380.8
102.5°	884.6	978.7	1085.5	1161.0	1236.4	1342.1	1346.7	1209.7	923.0	609.5	382.0
105°	1374.6	1446.5	1518.5	1537.6	1556.8	1541.7	1410.5	1169.1	860.3	579.3	387.8
107.5°	1685.7	1696.1	1697.3	1674.1	1650.9	1537.1	1342.1	1083.2	802.2	563.1	400.5
110°	1771.6	1749.5	1699.6	1652.0	1604.4	1455.8	1248.0	1003.1	762.7	558.4	416.8

TEST NUMBER: P1009221

CATALOG NUMBER: S122DIP-B675D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1748.4	1707.7	1633.4	1577.1	1520.8	1359.5	1162.1	947.3	737.2	559.6	434.2
115°	1681.0	1627.6	1545.2	1485.4	1425.6	1273.6	1094.8	903.2	719.8	564.2	451.6
117.5°	1596.3	1539.4	1454.7	1397.8	1340.9	1199.3	1039.0	873.0	710.5	571.2	470.2
120°	1508.1	1453.5	1372.2	1319.4	1266.6	1143.5	999.6	849.8	702.4	578.2	488.8
122.5°	1429.1	1375.7	1304.9	1258.4	1212.0	1097.1	968.2	830.1	697.7	586.3	505.0
125°	1358.3	1314.2	1246.9	1203.4	1159.8	1057.6	938.0	811.5	691.9	594.4	522.4
127.5°	1297.9	1256.1	1196.9	1156.3	1115.7	1018.1	907.9	794.1	688.4	602.5	538.7
130°	1243.4	1203.9	1147.0	1108.7	1070.4	978.7	878.8	776.7	686.1	611.8	553.8
132.5°	1190.0	1150.5	1094.8	1059.4	1024.0	941.5	851.0	762.7	685.0	621.1	568.9
135°	1131.9	1093.6	1043.7	1011.2	978.7	902.1	825.4	750.0	683.8	628.1	581.6
137.5°	1072.7	1039.0	991.4	962.4	933.4	870.7	804.5	740.7	683.8	635.0	592.1
140°	1012.3	982.2	945.0	919.4	893.9	840.5	784.8	732.6	682.6	639.7	600.2
142.5°	960.1	933.4	898.6	878.2	857.9	813.8	768.5	724.4	682.6	643.2	607.2
145°	909.0	889.3	861.4	844.6	827.8	791.8	753.5	717.5	680.3	645.5	613.0
147.5°	868.4	852.1	827.8	815.0	802.2	773.2	741.8	710.5	676.8	646.6	616.5
150°	831.2	817.3	799.9	789.4	779.0	754.6	729.1	701.2	673.3	645.5	618.8
152.5°	801.1	789.4	776.7	768.0	759.3	739.5	716.3	693.1	667.5	643.2	619.9
155°	774.3	766.2	753.5	747.1	740.7	723.3	704.7	682.6	660.6	640.8	621.1
157.5°	748.8	741.8	732.6	727.4	722.1	707.0	690.8	673.3	653.6	636.2	621.1
160°	725.6	719.8	711.7	707.6	703.5	690.8	678.0	662.9	646.6	632.7	621.1
162.5°	703.5	700.0	691.9	689.0	686.1	675.7	665.2	653.6	640.8	629.2	619.9
165°	682.6	678.0	673.3	671.0	668.7	660.6	652.5	643.2	632.7	624.6	617.6
167.5°	661.7	659.4	657.1	654.8	652.5	646.6	639.7	632.7	625.7	619.9	616.5
170°	645.5	642.0	640.8	639.6	638.5	633.9	630.4	624.6	619.9	616.5	614.1
172.5°	629.2	628.1	626.9	626.3	625.7	622.3	619.9	616.5	613.0	611.8	610.7
175°	617.6	616.5	616.5	615.9	615.3	614.1	613.0	609.5	608.3	607.2	608.3
177.5°	608.3	608.3	608.3	608.3	608.3	607.2	607.2	604.9	603.7	604.9	607.2
180°	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7

TEST NUMBER: P1009221

CATALOG NUMBER: S122DIP-B675D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1370.2	1365.0	1361.9	1364.0	1357.8	1342.4	1342.4	1347.6	1341.4	1335.3	1326.0
5°	1408.1	1397.9	1391.7	1390.7	1376.3	1351.7	1346.6	1341.4	1328.1	1313.7	1298.3
7.5°	1445.1	1426.6	1416.3	1409.2	1388.6	1356.8	1343.5	1332.2	1310.6	1289.1	1269.6
10°	1475.9	1449.2	1436.9	1425.6	1398.9	1358.9	1337.3	1316.8	1289.1	1261.4	1236.7
12.5°	1500.5	1469.7	1454.3	1437.9	1405.1	1352.7	1326.0	1293.2	1265.5	1228.5	1203.9
15°	1541.6	1477.9	1463.6	1448.2	1414.3	1342.4	1309.6	1272.7	1234.7	1185.4	1158.7
17.5°	1574.4	1489.2	1488.2	1455.3	1411.2	1338.3	1288.1	1239.8	1198.8	1149.5	1107.4
20°	1593.9	1506.7	1490.2	1456.4	1400.9	1310.6	1258.3	1204.9	1160.8	1101.3	1059.2
22.5°	1610.3	1531.3	1488.2	1447.1	1379.4	1301.4	1224.4	1174.1	1113.6	1048.9	1008.9
25°	1616.5	1536.4	1491.3	1444.1	1364.0	1274.7	1187.5	1133.1	1065.3	1006.8	952.4
27.5°	1617.5	1535.4	1480.0	1430.7	1342.4	1239.8	1150.5	1093.0	1018.1	950.4	896.0
30°	1607.2	1524.1	1473.8	1420.5	1321.9	1208.0	1105.4	1041.7	961.7	893.9	837.5
32.5°	1576.5	1501.5	1460.5	1402.0	1295.2	1163.9	1062.3	991.4	907.3	840.6	786.2
35°	1525.1	1473.8	1428.7	1374.3	1260.3	1122.8	1019.2	936.0	850.8	787.2	735.9
37.5°	1461.5	1433.8	1391.7	1338.3	1220.3	1085.9	970.9	878.5	793.4	731.8	681.5
40°	1375.3	1382.5	1341.4	1293.2	1173.1	1035.6	908.3	820.0	740.0	682.5	633.2
42.5°	1281.9	1311.7	1288.1	1241.9	1120.8	980.2	862.1	764.6	686.6	627.1	586.0
45°	1181.3	1232.6	1218.3	1184.4	1066.4	921.7	796.4	702.0	633.2	575.8	539.9
47.5°	1071.5	1144.4	1144.4	1119.7	1005.8	863.1	740.0	643.5	575.8	534.7	499.8
50°	959.6	1041.7	1055.1	1038.7	938.1	796.4	671.2	584.0	525.5	485.5	459.8
52.5°	842.6	938.1	962.7	954.5	866.2	732.8	614.8	529.6	476.2	441.3	418.7
55°	730.8	841.6	868.3	871.4	789.3	663.0	552.2	477.2	425.9	402.3	382.8
57.5°	625.0	731.8	761.5	766.7	711.3	599.4	493.7	428.0	381.8	362.3	346.9
60°	534.7	624.0	663.0	674.3	626.1	525.5	439.3	375.6	340.7	322.3	307.9
62.5°	460.8	532.7	573.7	576.8	555.2	460.8	382.8	329.5	299.7	283.3	276.1
65°	389.0	453.6	478.3	490.6	473.1	399.2	330.5	286.3	262.7	248.4	241.2
67.5°	331.5	372.6	393.1	409.5	392.1	336.6	281.2	245.3	227.8	213.5	209.4
70°	272.0	305.8	321.2	337.7	322.3	280.2	240.2	207.3	191.9	180.6	175.5
72.5°	217.6	244.3	258.6	268.9	259.7	224.8	191.9	169.3	158.1	149.8	146.8
75°	172.4	190.9	199.1	206.3	202.2	175.5	155.0	136.5	126.2	119.1	117.0
77.5°	131.4	144.7	154.0	156.0	150.9	133.4	116.0	104.7	96.5	92.4	90.3
80°	93.4	101.6	106.7	109.8	104.7	97.5	85.2	77.0	69.8	64.7	63.6
82.5°	62.6	66.7	70.8	69.8	67.7	61.6	54.4	50.3	47.2	43.1	43.1
85°	35.9	36.9	39.0	40.0	39.0	34.9	30.8	28.7	26.7	23.6	23.6
87.5°	15.4	16.4	16.4	17.4	15.4	15.4	13.3	11.3	11.3	10.3	9.2
90°	23.2	17.4	15.6	13.9	11.6	9.3	4.6	1.2	4.6	9.3	11.6
92.5°	92.9	61.5	55.2	48.8	39.5	33.7	24.4	17.4	24.4	33.7	39.5
95°	167.2	113.8	99.8	85.9	67.3	56.9	45.3	40.6	45.3	56.9	67.3
97.5°	215.9	147.4	131.8	116.1	95.2	80.1	67.3	60.4	67.3	80.1	95.2
100°	239.2	177.6	161.4	145.1	121.9	103.3	92.9	89.4	92.9	103.3	121.9
102.5°	260.1	204.3	188.0	171.8	147.4	128.9	118.4	116.1	118.4	128.9	147.4
105°	284.4	229.9	213.6	197.4	171.8	154.4	146.3	141.6	146.3	154.4	171.8
107.5°	308.8	255.4	239.2	222.9	197.4	181.1	173.0	169.5	173.0	181.1	197.4
110°	333.2	282.1	265.2	248.4	224.1	209.0	202.0	197.4	202.0	209.0	224.1

TEST NUMBER: P1009221

CATALOG NUMBER: S122DIP-B675D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	356.4	307.7	290.2	272.8	249.6	235.7	227.5	222.9	227.5	235.7	249.6
115°	380.8	330.9	315.2	299.5	276.3	262.4	255.4	249.6	255.4	262.4	276.3
117.5°	402.8	356.4	340.2	323.9	301.8	289.1	282.1	277.5	282.1	289.1	301.8
120°	426.1	380.8	364.6	348.3	325.1	314.6	307.7	303.0	307.7	314.6	325.1
122.5°	448.1	406.3	389.5	372.7	349.4	337.8	330.9	327.4	330.9	337.8	349.4
125°	470.2	428.4	412.2	395.9	372.7	358.7	351.8	348.3	351.8	358.7	372.7
127.5°	491.1	450.4	433.6	416.8	394.7	379.6	370.3	365.7	370.3	379.6	394.7
130°	509.7	469.0	452.8	436.5	413.3	397.0	385.4	380.8	385.4	397.0	413.3
132.5°	525.9	487.6	471.4	455.1	430.7	413.3	400.5	394.7	400.5	413.3	430.7
135°	541.0	503.8	487.6	471.3	444.6	427.2	413.3	408.7	413.3	427.2	444.6
137.5°	553.8	516.6	501.5	486.4	459.7	441.2	427.2	421.4	427.2	441.2	459.7
140°	564.2	529.4	514.3	499.2	473.7	455.1	441.2	436.5	441.2	455.1	473.7
142.5°	572.3	538.7	524.8	510.8	486.4	467.9	455.1	451.6	455.1	467.9	486.4
145°	580.5	549.1	536.4	523.6	500.4	483.0	471.3	466.7	471.3	483.0	500.4
147.5°	587.4	557.3	545.6	534.0	514.3	498.0	486.4	483.0	486.4	498.0	514.3
150°	592.1	565.4	555.0	544.5	527.1	512.0	502.7	499.2	502.7	512.0	527.1
152.5°	596.7	573.5	564.2	554.9	538.7	525.9	516.6	515.5	516.6	525.9	538.7
155°	601.4	581.6	572.9	564.2	551.4	538.7	531.7	530.6	531.7	538.7	551.4
157.5°	604.9	587.4	579.8	572.3	561.9	550.3	544.5	543.3	544.5	550.3	561.9
160°	607.2	593.2	586.8	580.5	571.2	561.9	557.3	556.1	557.3	561.9	571.2
162.5°	608.3	596.7	592.0	587.4	579.3	572.3	567.7	568.9	567.7	572.3	579.3
165°	609.5	599.0	595.6	592.1	586.3	579.3	577.0	578.2	577.0	579.3	586.3
167.5°	609.5	601.4	599.0	596.7	592.1	587.4	585.1	586.3	585.1	587.4	592.1
170°	608.3	602.5	600.8	599.0	596.7	593.2	592.1	594.4	592.1	593.2	596.7
172.5°	607.2	603.7	602.6	601.4	600.2	596.7	597.9	599.0	597.9	596.7	600.2
175°	606.0	603.7	603.1	602.5	602.5	600.2	601.4	602.5	601.4	600.2	602.5
177.5°	604.9	603.7	603.7	603.7	603.7	601.4	602.5	604.9	602.5	601.4	603.7
180°	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7

TEST NUMBER: P1009221

CATALOG NUMBER: S122DIP-B675D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1320.9	1326.0	1325.0	1314.7	1303.4	1294.2	1276.8	1278.8	1272.7	1273.7	1279.8
5°	1288.1	1288.1	1283.9	1269.6	1251.1	1240.8	1221.3	1216.2	1203.9	1202.9	1201.8
7.5°	1253.2	1248.0	1242.9	1222.4	1199.8	1183.4	1156.7	1150.5	1138.2	1130.0	1125.9
10°	1212.1	1204.9	1194.7	1171.1	1143.3	1122.8	1095.1	1086.9	1063.3	1053.0	1046.9
12.5°	1166.9	1162.8	1146.4	1126.9	1081.8	1059.2	1019.2	1027.4	1003.8	983.2	980.2
15°	1121.8	1106.4	1097.2	1065.3	1010.9	1000.7	968.9	952.4	930.9	914.5	914.5
17.5°	1077.7	1054.0	1033.5	999.7	959.6	930.9	907.3	899.1	872.4	856.0	852.9
20°	1019.2	992.5	987.3	939.1	911.4	879.6	857.0	836.5	817.0	809.8	804.6
22.5°	963.7	932.9	924.7	883.7	856.0	824.1	801.6	787.2	772.8	767.7	758.5
25°	904.2	885.7	873.4	829.3	798.5	768.7	753.3	743.1	729.7	728.7	722.5
27.5°	846.7	829.3	817.0	774.9	752.3	724.6	712.3	701.0	693.8	690.7	687.6
30°	797.5	778.0	763.6	732.8	705.1	682.5	672.3	665.1	661.0	655.8	654.8
32.5°	743.1	731.8	712.3	688.7	667.1	645.6	639.4	634.3	628.1	626.1	625.0
35°	696.9	681.5	669.2	642.5	633.2	614.8	607.6	603.5	595.3	593.2	591.2
37.5°	651.7	637.4	624.0	607.6	590.1	579.9	575.8	569.6	565.5	566.5	564.5
40°	606.6	595.3	585.0	567.6	557.3	552.2	544.0	537.8	535.7	536.8	535.7
42.5°	562.4	552.2	546.0	532.7	522.4	517.3	512.1	506.0	509.1	509.1	512.1
45°	522.4	513.2	509.1	498.8	492.6	484.4	479.3	478.3	482.4	481.4	481.4
47.5°	481.4	478.3	473.1	463.9	455.7	450.6	449.5	449.5	453.6	455.7	454.7
50°	449.5	443.4	437.2	430.0	423.9	421.8	418.7	420.8	424.9	424.9	427.0
52.5°	409.5	405.4	403.4	397.2	393.1	393.1	393.1	394.1	397.2	400.3	399.2
55°	374.6	371.5	369.5	366.4	361.3	362.3	361.3	363.3	366.4	369.5	371.5
57.5°	337.7	336.6	334.6	329.5	329.5	328.4	331.5	332.5	337.7	339.7	342.8
60°	304.8	301.7	301.7	297.6	297.6	297.6	300.7	303.8	307.9	308.9	311.0
62.5°	269.9	269.9	268.9	265.8	265.8	268.9	269.9	274.0	276.1	276.1	279.2
65°	237.1	236.1	235.0	236.1	237.1	237.1	240.2	242.2	244.3	245.3	246.3
67.5°	204.2	203.2	205.3	204.2	206.3	210.4	209.4	212.5	215.5	215.5	216.6
70°	173.5	175.5	174.5	176.5	175.5	177.6	180.6	181.7	181.7	182.7	185.8
72.5°	144.7	144.7	144.7	143.7	144.7	146.8	148.8	149.8	151.9	152.9	156.0
75°	117.0	117.0	114.9	117.0	117.0	119.1	121.1	121.1	121.1	123.2	126.2
77.5°	88.3	89.3	88.3	90.3	90.3	91.3	93.4	92.4	94.4	95.4	96.5
80°	64.7	63.6	63.6	63.6	64.7	64.7	66.7	67.7	67.7	70.8	68.8
82.5°	41.1	42.1	41.1	42.1	42.1	43.1	42.1	43.1	44.1	46.2	45.2
85°	23.6	22.6	22.6	23.6	22.6	22.6	23.6	22.6	23.6	22.6	23.6
87.5°	9.2	8.2	8.2	8.2	8.2	7.2	7.2	6.2	6.2	6.2	5.1
90°	13.9	15.6	17.4	23.2	31.3	38.3	39.5	38.3	37.2	34.8	37.2
92.5°	48.8	55.2	61.5	92.9	137.0	176.5	178.8	149.8	117.3	99.8	87.1
95°	85.9	99.8	113.8	167.2	268.2	402.8	455.1	398.2	304.2	233.3	184.6
97.5°	116.1	131.8	147.4	215.9	356.4	573.5	741.8	747.6	622.3	496.9	379.6
100°	145.1	161.4	177.6	239.2	380.8	631.6	917.1	1084.3	1059.9	916.0	756.9
102.5°	171.8	188.0	204.3	260.1	382.0	609.5	923.0	1209.7	1346.7	1342.1	1236.4
105°	197.4	213.6	229.9	284.4	387.8	579.3	860.3	1169.1	1410.5	1541.7	1556.8
107.5°	222.9	239.2	255.4	308.8	400.5	563.1	802.2	1083.2	1342.1	1537.1	1650.9
110°	248.4	265.2	282.1	333.2	416.8	558.4	762.7	1003.1	1248.0	1455.8	1604.4

TEST NUMBER: P1009221

CATALOG NUMBER: S122DIP-B675D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	272.8	290.2	307.7	356.4	434.2	559.6	737.2	947.3	1162.1	1359.5	1520.8
115°	299.5	315.2	330.9	380.8	451.6	564.2	719.8	903.2	1094.8	1273.6	1425.6
117.5°	323.9	340.2	356.4	402.8	470.2	571.2	710.5	873.0	1039.0	1199.3	1340.9
120°	348.3	364.6	380.8	426.1	488.8	578.2	702.4	849.8	999.6	1143.5	1266.6
122.5°	372.7	389.5	406.3	448.1	505.0	586.3	697.7	830.1	968.2	1097.1	1212.0
125°	395.9	412.2	428.4	470.2	522.4	594.4	691.9	811.5	938.0	1057.6	1159.8
127.5°	416.8	433.6	450.4	491.1	538.7	602.5	688.4	794.1	907.9	1018.1	1115.7
130°	436.5	452.8	469.0	509.7	553.8	611.8	686.1	776.7	878.8	978.7	1070.4
132.5°	455.1	471.4	487.6	525.9	568.9	621.1	685.0	762.7	851.0	941.5	1024.0
135°	471.3	487.6	503.8	541.0	581.6	628.1	683.8	750.0	825.4	902.1	978.7
137.5°	486.4	501.5	516.6	553.8	592.1	635.0	683.8	740.7	804.5	870.7	933.4
140°	499.2	514.3	529.4	564.2	600.2	639.7	682.6	732.6	784.8	840.5	893.9
142.5°	510.8	524.8	538.7	572.3	607.2	643.2	682.6	724.4	768.5	813.8	857.9
145°	523.6	536.4	549.1	580.5	613.0	645.5	680.3	717.5	753.5	791.8	827.8
147.5°	534.0	545.6	557.3	587.4	616.5	646.6	676.8	710.5	741.8	773.2	802.2
150°	544.5	555.0	565.4	592.1	618.8	645.5	673.3	701.2	729.1	754.6	779.0
152.5°	554.9	564.2	573.5	596.7	619.9	643.2	667.5	693.1	716.3	739.5	759.3
155°	564.2	572.9	581.6	601.4	621.1	640.8	660.6	682.6	704.7	723.3	740.7
157.5°	572.3	579.8	587.4	604.9	621.1	636.2	653.6	673.3	690.8	707.0	722.1
160°	580.5	586.8	593.2	607.2	621.1	632.7	646.6	662.9	678.0	690.8	703.5
162.5°	587.4	592.0	596.7	608.3	619.9	629.2	640.8	653.6	665.2	675.7	686.1
165°	592.1	595.6	599.0	609.5	617.6	624.6	632.7	643.2	652.5	660.6	668.7
167.5°	596.7	599.0	601.4	609.5	616.5	619.9	625.7	632.7	639.7	646.6	652.5
170°	599.0	600.8	602.5	608.3	614.1	616.5	619.9	624.6	630.4	633.9	638.5
172.5°	601.4	602.6	603.7	607.2	610.7	611.8	613.0	616.5	619.9	622.3	625.7
175°	602.5	603.1	603.7	606.0	608.3	607.2	608.3	609.5	613.0	614.1	615.3
177.5°	603.7	603.7	603.7	604.9	607.2	604.9	603.7	604.9	607.2	607.2	608.3
180°	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7

TEST NUMBER: P1009221

CATALOG NUMBER: S122DIP-B675D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1272.7	1275.7	1268.6	1266.5	1268.6	1261.4	1263.4	1265.5	1265.5	1268.6	1270.6
5°	1198.8	1194.7	1187.5	1185.4	1183.4	1186.4	1184.4	1187.5	1188.5	1195.7	1196.7
7.5°	1125.9	1119.7	1113.6	1107.4	1105.4	1100.2	1105.4	1105.4	1112.5	1110.5	1115.6
10°	1039.7	1038.7	1030.4	1027.4	1023.3	1015.0	1026.3	1023.3	1028.4	1037.6	1039.7
12.5°	976.0	964.8	969.9	955.5	960.7	952.4	953.5	953.5	961.7	962.7	960.7
15°	915.5	906.3	892.9	886.8	883.7	879.6	892.9	893.9	887.8	902.2	897.0
17.5°	853.9	853.9	841.6	838.5	830.3	834.4	832.4	833.4	831.3	841.6	846.7
20°	800.5	795.4	791.3	792.3	782.1	780.0	778.0	780.0	787.2	794.4	796.4
22.5°	757.4	754.4	744.1	746.1	737.9	741.0	739.0	744.1	745.1	745.1	752.3
25°	716.4	712.3	713.3	709.2	706.1	706.1	703.0	706.1	710.2	712.3	713.3
27.5°	685.6	682.5	677.4	674.3	676.4	671.2	675.3	678.4	678.4	676.4	678.4
30°	648.6	650.7	650.7	640.4	644.5	642.5	645.6	647.6	647.6	648.6	646.6
32.5°	624.0	617.9	616.8	615.8	615.8	611.7	611.7	614.8	615.8	616.8	619.9
35°	591.2	591.2	586.0	589.1	585.0	586.0	585.0	586.0	588.1	585.0	588.1
37.5°	561.4	562.4	560.4	562.4	563.5	561.4	559.4	563.5	561.4	561.4	559.4
40°	535.7	534.7	535.7	535.7	535.7	536.8	534.7	534.7	534.7	532.7	530.6
42.5°	514.2	508.0	510.1	511.1	508.0	508.0	509.1	508.0	511.1	505.0	505.0
45°	483.4	481.4	482.4	482.4	484.4	481.4	483.4	484.4	481.4	480.3	478.3
47.5°	455.7	457.7	455.7	457.7	457.7	459.8	455.7	456.7	457.7	453.6	450.6
50°	428.0	428.0	431.1	430.0	431.1	429.0	429.0	428.0	429.0	427.0	423.9
52.5°	402.3	399.2	404.4	403.4	402.3	401.3	400.3	401.3	399.2	397.2	397.2
55°	370.5	370.5	373.6	374.6	374.6	372.6	370.5	371.5	370.5	369.5	368.5
57.5°	344.8	340.7	342.8	343.8	343.8	340.7	342.8	340.7	340.7	341.8	338.7
60°	312.0	312.0	310.0	313.0	313.0	311.0	311.0	312.0	310.0	308.9	307.9
62.5°	277.1	278.1	281.2	282.2	283.3	281.2	279.2	280.2	280.2	277.1	278.1
65°	247.3	249.4	253.5	252.5	250.4	251.5	249.4	250.4	247.3	248.4	245.3
67.5°	218.6	217.6	218.6	218.6	220.7	219.6	217.6	217.6	216.6	219.6	216.6
70°	187.8	187.8	187.8	187.8	188.8	189.9	187.8	185.8	186.8	184.7	183.7
72.5°	156.0	157.0	156.0	158.1	155.0	157.0	157.0	156.0	155.0	155.0	155.0
75°	126.2	128.3	125.2	126.2	125.2	127.3	126.2	126.2	124.2	123.2	124.2
77.5°	96.5	97.5	95.4	96.5	95.4	96.5	96.5	95.4	95.4	95.4	95.4
80°	68.8	69.8	68.8	67.7	66.7	68.8	66.7	67.7	68.8	67.7	69.8
82.5°	44.1	44.1	43.1	44.1	42.1	42.1	43.1	43.1	42.1	44.1	42.1
85°	21.6	21.6	23.6	21.6	20.5	20.5	20.5	21.6	20.5	22.6	21.6
87.5°	5.1	4.1	5.1	5.1	4.1	4.1	5.1	4.1	5.1	6.2	4.1
90°	37.8	38.3	38.3	38.3	38.3	38.3	38.3	38.3	38.3	38.3	37.8
92.5°	82.4	77.8	76.6	72.0	73.1	70.8	73.1	72.0	76.6	77.8	82.4
95°	171.8	159.0	144.0	134.7	131.2	132.3	131.2	134.7	144.0	159.0	171.8
97.5°	344.8	310.0	264.7	241.5	228.7	221.7	228.7	241.5	264.7	310.0	344.8
100°	686.7	616.5	520.1	470.2	436.5	415.6	436.5	470.2	520.1	616.5	686.7
102.5°	1161.0	1085.5	978.7	884.6	840.5	810.3	840.5	884.6	978.7	1085.5	1161.0
105°	1537.6	1518.5	1446.5	1374.6	1324.6	1308.4	1324.6	1374.6	1446.5	1518.5	1537.6
107.5°	1674.1	1697.3	1696.1	1685.7	1670.6	1643.9	1670.6	1685.7	1696.1	1697.3	1674.1
110°	1652.0	1699.6	1749.5	1771.6	1782.0	1780.9	1782.0	1771.6	1749.5	1699.6	1652.0

TEST NUMBER: P1009221

CATALOG NUMBER: S122DIP-B675D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1577.1	1633.4	1707.7	1748.4	1770.4	1778.6	1770.4	1748.4	1707.7	1633.4	1577.1
115°	1485.4	1545.2	1627.6	1681.0	1711.2	1721.7	1711.2	1681.0	1627.6	1545.2	1485.4
117.5°	1397.8	1454.7	1539.4	1596.3	1627.6	1635.8	1627.6	1596.3	1539.4	1454.7	1397.8
120°	1319.4	1372.2	1453.5	1508.1	1541.7	1553.3	1541.7	1508.1	1453.5	1372.2	1319.4
122.5°	1258.4	1304.9	1375.7	1429.1	1458.1	1467.4	1458.1	1429.1	1375.7	1304.9	1258.4
125°	1203.4	1246.9	1314.2	1358.3	1387.3	1396.6	1387.3	1358.3	1314.2	1246.9	1203.4
127.5°	1156.3	1196.9	1256.1	1297.9	1323.5	1330.4	1323.5	1297.9	1256.1	1196.9	1156.3
130°	1108.7	1147.0	1203.9	1243.4	1266.6	1275.9	1266.6	1243.4	1203.9	1147.0	1108.7
132.5°	1059.4	1094.8	1150.5	1190.0	1210.9	1219.0	1210.9	1190.0	1150.5	1094.8	1059.4
135°	1011.2	1043.7	1093.6	1131.9	1152.8	1157.5	1152.8	1131.9	1093.6	1043.7	1011.2
137.5°	962.4	991.4	1039.0	1072.7	1091.3	1098.3	1091.3	1072.7	1039.0	991.4	962.4
140°	919.4	945.0	982.2	1012.3	1029.8	1036.7	1029.8	1012.3	982.2	945.0	919.4
142.5°	878.2	898.6	933.4	960.1	975.2	975.2	975.2	960.1	933.4	898.6	878.2
145°	844.6	861.4	889.3	909.0	920.6	924.1	920.6	909.0	889.3	861.4	844.6
147.5°	815.0	827.8	852.1	868.4	876.5	878.8	876.5	868.4	852.1	827.8	815.0
150°	789.4	799.9	817.3	831.2	838.2	839.4	838.2	831.2	817.3	799.9	789.4
152.5°	768.0	776.7	789.4	801.1	805.7	805.7	805.7	801.1	789.4	776.7	768.0
155°	747.1	753.5	766.2	774.3	779.0	776.7	779.0	774.3	766.2	753.5	747.1
157.5°	727.4	732.6	741.8	748.8	751.1	751.1	751.1	748.8	741.8	732.6	727.4
160°	707.6	711.7	719.8	725.6	726.8	726.8	726.8	725.6	719.8	711.7	707.6
162.5°	689.0	691.9	700.0	703.5	704.7	703.5	704.7	703.5	700.0	691.9	689.0
165°	671.0	673.3	678.0	682.6	682.6	681.5	682.6	682.6	678.0	673.3	671.0
167.5°	654.8	657.1	659.4	661.7	661.7	660.6	661.7	661.7	659.4	657.1	654.8
170°	639.6	640.8	642.0	645.5	644.3	642.0	644.3	645.5	642.0	640.8	639.6
172.5°	626.3	626.9	628.1	629.2	628.1	626.9	628.1	629.2	628.1	626.9	626.3
175°	615.9	616.5	616.5	617.6	616.5	614.1	616.5	617.6	616.5	616.5	615.9
177.5°	608.3	608.3	608.3	608.3	607.2	604.9	607.2	608.3	608.3	608.3	608.3
180°	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7

TEST NUMBER: P1009221

CATALOG NUMBER: S122DIP-B675D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1267.5	1275.7	1272.7	1261.4	1274.7	1274.7	1283.9	1283.9	1295.2	1299.3	1305.5
5°	1195.7	1201.8	1207.0	1201.8	1211.1	1225.4	1233.7	1240.8	1256.2	1262.4	1271.6
7.5°	1118.7	1130.0	1135.1	1135.1	1150.5	1166.9	1183.4	1193.6	1215.2	1223.4	1232.6
10°	1043.8	1057.1	1067.4	1066.4	1092.0	1102.3	1122.8	1146.4	1168.0	1180.3	1193.6
12.5°	964.8	971.9	986.3	1006.8	1013.0	1031.5	1055.1	1084.8	1123.8	1135.1	1154.6
15°	899.1	918.6	929.9	939.1	953.5	970.9	996.6	1025.3	1064.3	1088.9	1109.5
17.5°	843.6	869.3	876.5	874.4	892.9	919.6	949.4	970.9	1005.8	1035.6	1055.1
20°	798.5	808.8	821.1	826.2	840.6	869.3	898.0	922.7	951.4	975.0	997.6
22.5°	753.3	761.5	771.8	781.0	792.3	808.8	836.5	867.3	895.0	917.5	943.2
25°	716.4	721.5	730.8	737.9	750.3	761.5	781.0	814.9	847.8	861.1	883.7
27.5°	680.5	684.6	690.7	698.9	705.1	716.4	733.8	761.5	795.4	808.8	839.5
30°	648.6	651.7	657.9	662.0	665.1	678.4	691.8	713.3	739.0	757.4	780.0
32.5°	618.9	622.0	628.1	629.1	633.2	640.4	652.8	672.3	694.8	710.2	729.7
35°	586.0	588.1	594.2	596.3	599.4	605.5	614.8	629.1	649.7	661.0	678.4
37.5°	560.4	559.4	563.5	566.5	570.6	573.7	576.8	591.2	606.6	616.8	630.2
40°	532.7	530.6	531.6	535.7	537.8	541.9	541.9	556.3	566.5	574.7	585.0
42.5°	505.0	503.9	501.9	503.9	506.0	507.0	508.0	518.3	528.6	535.7	547.0
45°	477.2	476.2	474.2	475.2	475.2	477.2	480.3	484.4	491.6	497.8	503.9
47.5°	451.6	449.5	446.5	445.4	447.5	447.5	447.5	451.6	458.8	460.8	467.0
50°	424.9	421.8	417.7	415.7	415.7	414.6	416.7	417.7	423.9	425.9	431.1
52.5°	396.2	394.1	390.0	385.9	386.9	384.9	385.9	386.9	389.0	392.1	395.1
55°	367.4	363.3	360.2	359.2	356.1	356.1	353.1	357.2	356.1	357.2	361.3
57.5°	339.7	335.6	330.5	328.4	325.3	324.3	322.3	321.2	322.3	325.3	328.4
60°	306.9	304.8	301.7	298.7	296.6	293.5	291.5	291.5	290.5	290.5	291.5
62.5°	275.1	274.0	269.9	268.9	266.8	264.8	261.7	259.7	259.7	261.7	262.7
65°	244.3	243.2	240.2	239.1	234.0	232.0	230.9	229.9	227.8	227.8	227.8
67.5°	215.5	212.5	212.5	207.3	203.2	201.2	199.1	198.1	198.1	198.1	199.1
70°	183.7	183.7	180.6	177.6	173.5	174.5	171.4	168.3	168.3	166.3	167.3
72.5°	152.9	151.9	148.8	147.8	144.7	141.6	139.6	141.6	138.6	137.5	138.6
75°	123.2	122.1	120.1	118.0	119.1	116.0	112.9	111.9	111.9	109.8	109.8
77.5°	94.4	96.5	92.4	91.3	89.3	87.2	86.2	85.2	85.2	85.2	87.2
80°	65.7	66.7	66.7	64.7	65.7	62.6	62.6	62.6	59.5	60.6	61.6
82.5°	42.1	42.1	41.1	42.1	41.1	41.1	40.0	40.0	39.0	39.0	40.0
85°	23.6	22.6	21.6	23.6	22.6	22.6	21.6	21.6	21.6	21.6	21.6
87.5°	5.1	6.2	6.2	6.2	6.2	7.2	7.2	7.2	8.2	8.2	8.2
90°	37.2	34.8	37.2	38.3	39.5	38.3	31.3	23.2	17.4	15.6	13.9
92.5°	87.1	99.8	117.3	149.8	178.8	176.5	137.0	92.9	61.5	55.2	48.8
95°	184.6	233.3	304.2	398.2	455.1	402.8	268.2	167.2	113.8	99.8	85.9
97.5°	379.6	496.9	622.3	747.6	741.8	573.5	356.4	215.9	147.4	131.8	116.1
100°	756.9	916.0	1059.9	1084.3	917.1	631.6	380.8	239.2	177.6	161.4	145.1
102.5°	1236.4	1342.1	1346.7	1209.7	923.0	609.5	382.0	260.1	204.3	188.0	171.8
105°	1556.8	1541.7	1410.5	1169.1	860.3	579.3	387.8	284.4	229.9	213.6	197.4
107.5°	1650.9	1537.1	1342.1	1083.2	802.2	563.1	400.5	308.8	255.4	239.2	222.9
110°	1604.4	1455.8	1248.0	1003.1	762.7	558.4	416.8	333.2	282.1	265.2	248.4

TEST NUMBER: P1009221

CATALOG NUMBER: S122DIP-B675D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1520.8	1359.5	1162.1	947.3	737.2	559.6	434.2	356.4	307.7	290.2	272.8
115°	1425.6	1273.6	1094.8	903.2	719.8	564.2	451.6	380.8	330.9	315.2	299.5
117.5°	1340.9	1199.3	1039.0	873.0	710.5	571.2	470.2	402.8	356.4	340.2	323.9
120°	1266.6	1143.5	999.6	849.8	702.4	578.2	488.8	426.1	380.8	364.6	348.3
122.5°	1212.0	1097.1	968.2	830.1	697.7	586.3	505.0	448.1	406.3	389.5	372.7
125°	1159.8	1057.6	938.0	811.5	691.9	594.4	522.4	470.2	428.4	412.2	395.9
127.5°	1115.7	1018.1	907.9	794.1	688.4	602.5	538.7	491.1	450.4	433.6	416.8
130°	1070.4	978.7	878.8	776.7	686.1	611.8	553.8	509.7	469.0	452.8	436.5
132.5°	1024.0	941.5	851.0	762.7	685.0	621.1	568.9	525.9	487.6	471.4	455.1
135°	978.7	902.1	825.4	750.0	683.8	628.1	581.6	541.0	503.8	487.6	471.3
137.5°	933.4	870.7	804.5	740.7	683.8	635.0	592.1	553.8	516.6	501.5	486.4
140°	893.9	840.5	784.8	732.6	682.6	639.7	600.2	564.2	529.4	514.3	499.2
142.5°	857.9	813.8	768.5	724.4	682.6	643.2	607.2	572.3	538.7	524.8	510.8
145°	827.8	791.8	753.5	717.5	680.3	645.5	613.0	580.5	549.1	536.4	523.6
147.5°	802.2	773.2	741.8	710.5	676.8	646.6	616.5	587.4	557.3	545.6	534.0
150°	779.0	754.6	729.1	701.2	673.3	645.5	618.8	592.1	565.4	555.0	544.5
152.5°	759.3	739.5	716.3	693.1	667.5	643.2	619.9	596.7	573.5	564.2	554.9
155°	740.7	723.3	704.7	682.6	660.6	640.8	621.1	601.4	581.6	572.9	564.2
157.5°	722.1	707.0	690.8	673.3	653.6	636.2	621.1	604.9	587.4	579.8	572.3
160°	703.5	690.8	678.0	662.9	646.6	632.7	621.1	607.2	593.2	586.8	580.5
162.5°	686.1	675.7	665.2	653.6	640.8	629.2	619.9	608.3	596.7	592.0	587.4
165°	668.7	660.6	652.5	643.2	632.7	624.6	617.6	609.5	599.0	595.6	592.1
167.5°	652.5	646.6	639.7	632.7	625.7	619.9	616.5	609.5	601.4	599.0	596.7
170°	638.5	633.9	630.4	624.6	619.9	616.5	614.1	608.3	602.5	600.8	599.0
172.5°	625.7	622.3	619.9	616.5	613.0	611.8	610.7	607.2	603.7	602.6	601.4
175°	615.3	614.1	613.0	609.5	608.3	607.2	608.3	606.0	603.7	603.1	602.5
177.5°	608.3	607.2	607.2	604.9	603.7	604.9	607.2	604.9	603.7	603.7	603.7
180°	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7	603.7

TEST NUMBER: P1009221

CATALOG NUMBER: S122DIP-B675D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1335.3	1335.3	1335.3	1335.3
2.5°	1310.6	1310.6	1326.0	1342.4
5°	1281.9	1289.1	1313.7	1336.3
7.5°	1254.2	1266.5	1297.3	1326.0
10°	1220.3	1236.7	1274.7	1308.6
12.5°	1187.5	1202.9	1247.0	1285.0
15°	1141.3	1160.8	1208.0	1255.2
17.5°	1095.1	1114.6	1172.1	1227.5
20°	1040.7	1066.4	1131.0	1204.9
22.5°	990.4	1022.2	1094.1	1153.6
25°	935.0	984.3	1051.0	1127.9
27.5°	885.7	935.0	1002.7	1080.7
30°	830.3	880.6	950.4	1022.2
32.5°	776.9	823.1	890.9	979.1
35°	721.5	765.6	831.3	920.6
37.5°	671.2	714.3	786.2	868.3
40°	622.0	667.1	728.7	810.8
42.5°	575.8	615.8	671.2	753.3
45°	533.7	562.4	613.7	690.7
47.5°	489.6	515.2	562.4	639.4
50°	448.5	470.1	511.1	583.0
52.5°	408.5	427.0	464.9	522.4
55°	372.6	390.0	417.7	474.2
57.5°	335.6	349.0	375.6	420.8
60°	299.7	312.0	333.6	370.5
62.5°	263.8	274.0	294.6	324.3
65°	232.0	240.2	255.6	281.2
67.5°	201.2	206.3	218.6	239.1
70°	171.4	175.5	185.8	202.2
72.5°	139.6	143.7	155.0	166.3
75°	112.9	113.9	122.1	131.4
77.5°	88.3	87.2	93.4	100.6
80°	60.6	63.6	68.8	71.8
82.5°	41.1	42.1	44.1	46.2
85°	22.6	23.6	23.6	26.7
87.5°	9.2	10.3	10.3	11.3
90°	11.6	9.3	4.6	1.2
92.5°	39.5	33.7	24.4	17.4
95°	67.3	56.9	45.3	40.6
97.5°	95.2	80.1	67.3	60.4
100°	121.9	103.3	92.9	89.4
102.5°	147.4	128.9	118.4	116.1
105°	171.8	154.4	146.3	141.6
107.5°	197.4	181.1	173.0	169.5
110°	224.1	209.0	202.0	197.4



TEST NUMBER: P1009221

CATALOG NUMBER: S122DIP-B675D1080UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	249.6	235.7	227.5	222.9
115°	276.3	262.4	255.4	249.6
117.5°	301.8	289.1	282.1	277.5
120°	325.1	314.6	307.7	303.0
122.5°	349.4	337.8	330.9	327.4
125°	372.7	358.7	351.8	348.3
127.5°	394.7	379.6	370.3	365.7
130°	413.3	397.0	385.4	380.8
132.5°	430.7	413.3	400.5	394.7
135°	444.6	427.2	413.3	408.7
137.5°	459.7	441.2	427.2	421.4
140°	473.7	455.1	441.2	436.5
142.5°	486.4	467.9	455.1	451.6
145°	500.4	483.0	471.3	466.7
147.5°	514.3	498.0	486.4	483.0
150°	527.1	512.0	502.7	499.2
152.5°	538.7	525.9	516.6	515.5
155°	551.4	538.7	531.7	530.6
157.5°	561.9	550.3	544.5	543.3
160°	571.2	561.9	557.3	556.1
162.5°	579.3	572.3	567.7	568.9
165°	586.3	579.3	577.0	578.2
167.5°	592.1	587.4	585.1	586.3
170°	596.7	593.2	592.1	594.4
172.5°	600.2	596.7	597.9	599.0
175°	602.5	600.2	601.4	602.5
177.5°	603.7	601.4	602.5	604.9
180°	603.7	603.7	603.7	603.7

(END OF REPORT)