

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009638

Luminaire Tested: S122DIP-B865D925UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009638
REPORT IS A COMBINATION OF REPORTS P985002 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D925UB40-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7326.0 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009638

CATALOG NUMBER: S122DIP-B865D925UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1009638

CATALOG NUMBER: S122DIP-B865D925UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	99	94	91	87	91	88	84	81	74	72	70	63	61	59	52	50	49
2	90	83	77	72	83	77	72	68	66	62	59	56	53	50	46	44	42
3	83	73	66	61	76	68	62	57	59	54	50	50	46	43	41	39	37
4	76	65	58	52	70	61	54	49	52	47	43	44	41	37	37	34	32
5	70	58	51	45	64	55	48	42	47	42	38	40	36	33	34	31	28
6	64	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25
7	60	48	40	35	55	45	38	33	39	33	29	33	29	26	28	25	23
8	56	43	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20
9	52	40	32	28	48	37	31	26	33	27	24	28	24	21	24	21	18
10	48	37	30	25	45	34	28	24	30	25	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27013	27013	27013	27013
5°	27077	28801	27180	22914
10°	26763	31441	26931	18891
15°	26114	33163	26477	15913
20°	25706	31139	25706	13832
25°	24887	26752	25001	12368
30°	23539	21029	23987	11203
35°	22345	14541	22718	10251
40°	20972	10979	21211	9491
45°	19278	9022	19595	8671
50°	17816	7919	17847	7938
55°	16148	6748	16251	7141
60°	14368	5636	14568	6232
65°	12776	4584	13011	5323
70°	11191	3597	11476	4294
75°	9392	2611	9762	3112
80°	7329	1655	7856	1848
85°	4817	832	5184	616

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 27922 cd/sqm

TEST NUMBER: P1009638

CATALOG NUMBER: S122DIP-B865D925UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	2.2
10°-20°	473.1	6.5
20°-30°	686.6	9.4
30°-40°	723.8	9.9
40°-50°	640.5	8.7
50°-60°	511.4	7.0
60°-70°	347.4	4.7
70°-80°	177.7	2.4
80°-90°	45.3	0.6
90°-100°	199.1	2.7
100°-110°	701.3	9.6
110°-120°	736.6	10.1
120°-130°	606.0	8.3
130°-140°	486.8	6.6
140°-150°	367.7	5.0
150°-160°	258.5	3.5
160°-170°	152.2	2.1
170°-180°	49.5	0.7
0°-30°	1322.2	18.0
0°-40°	2046.0	27.9
0°-60°	3197.9	43.7
0°-90°	3768.3	51.4
90°-120°	1637.0	22.3
90°-150°	3097.5	42.3
90°-180°	3558.0	48.6
0°-180°	7326.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1706	1706	1706	1706	1706	
5°	1708	1906	1714	1516	1708	162
15°	1604	2343	1626	1124	1604	453
25°	1442	1952	1448	902	1442	659
35°	1177	1062	1196	749	1177	736
45°	883	640	897	615	883	685
55°	606	450	610	476	606	541
65°	359	277	366	321	359	357
75°	168	136	174	163	168	180
85°	34	35	37	26	34	40
90°	1	32	1	32	1	4
95°	34	112	34	112	34	36
105°	120	1107	120	1107	120	127
115°	211	1457	211	1457	211	209
125°	295	1182	295	1182	295	262
135°	346	980	346	980	346	267
145°	395	782	395	782	395	248
155°	449	657	449	657	449	207
165°	489	577	489	577	489	138
175°	510	520	510	520	510	48
180°	511	511	511	511	511	

TEST NUMBER: P1009638

CATALOG NUMBER: S122DIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1715.7	1719.6	1726.1	1727.5	1740.6	1751.1	1762.9	1762.9	1766.8	1765.5	1755.0
5°	1707.8	1719.6	1736.6	1751.1	1774.7	1785.2	1800.9	1812.7	1823.2	1831.1	1829.8
7.5°	1694.7	1715.7	1740.6	1768.1	1799.6	1818.0	1840.3	1861.2	1875.7	1888.8	1898.0
10°	1672.4	1707.8	1741.9	1778.6	1819.3	1844.2	1870.4	1898.0	1920.3	1945.2	1968.8
12.5°	1642.2	1693.4	1735.3	1783.9	1833.7	1861.2	1903.2	1924.2	1967.5	2030.5	2047.5
15°	1604.2	1673.7	1713.0	1774.7	1840.3	1862.6	1920.3	1954.4	2043.6	2082.9	2130.1
17.5°	1568.7	1646.1	1698.6	1769.4	1833.7	1877.0	1933.4	2002.9	2077.7	2134.1	2186.5
20°	1539.9	1614.7	1677.6	1756.3	1837.6	1892.7	1951.8	2035.7	2117.0	2174.7	2215.4
22.5°	1474.3	1570.1	1643.5	1731.4	1829.8	1905.8	1962.2	2054.1	2141.9	2177.4	2212.8
25°	1441.5	1524.2	1609.4	1709.1	1824.5	1915.0	1963.6	2065.9	2143.3	2156.4	2164.2
27.5°	1381.2	1474.3	1574.0	1688.1	1823.2	1899.3	1960.9	2054.1	2115.7	2106.5	2082.9
30°	1306.4	1420.5	1530.7	1654.0	1804.8	1887.5	1945.2	2030.5	2061.9	2014.7	1972.7
32.5°	1251.3	1358.9	1480.9	1623.8	1783.9	1862.6	1919.0	1985.9	1992.4	1907.2	1836.3
35°	1176.6	1295.9	1433.6	1584.5	1748.4	1819.3	1871.7	1912.4	1880.9	1761.6	1677.6
37.5°	1109.7	1227.7	1374.6	1528.1	1699.9	1769.4	1811.4	1818.0	1740.6	1635.6	1512.3
40°	1036.2	1158.2	1311.7	1473.0	1646.1	1706.5	1732.7	1713.0	1601.5	1479.6	1336.6
42.5°	962.8	1083.4	1248.7	1414.0	1577.9	1629.1	1639.6	1585.8	1449.4	1306.4	1141.1
45°	882.7	1008.7	1173.9	1340.5	1499.2	1528.1	1529.4	1452.0	1290.7	1141.1	987.7
47.5°	817.2	933.9	1097.9	1264.4	1398.2	1417.9	1410.0	1320.8	1145.1	977.2	843.4
50°	745.0	856.5	1019.2	1183.1	1297.2	1302.5	1282.8	1155.6	983.7	830.3	724.0
52.5°	667.6	780.4	930.0	1087.4	1189.7	1181.8	1143.8	1007.4	846.0	718.8	637.5
55°	606.0	705.7	846.0	999.5	1071.6	1049.3	1007.4	868.3	741.1	633.5	562.7
57.5°	537.8	625.7	763.4	897.2	939.2	918.2	876.2	746.3	628.3	547.0	499.7
60°	473.5	553.5	674.2	785.7	818.5	796.2	747.6	630.9	545.7	477.4	442.0
62.5°	414.5	484.0	585.0	687.3	700.4	678.1	636.2	541.7	468.3	414.5	388.3
65°	359.4	425.0	506.3	583.7	595.5	571.9	528.6	460.4	398.7	364.6	339.7
67.5°	305.6	358.1	430.2	486.6	493.2	470.9	435.5	380.4	342.3	305.6	287.3
70°	258.4	297.7	354.1	400.1	402.7	381.7	363.3	313.5	284.6	258.4	244.0
72.5°	212.5	240.0	283.3	317.4	318.7	305.6	288.6	257.1	232.2	213.8	199.4
75°	167.9	191.5	217.7	247.9	246.6	236.1	223.0	203.3	182.3	170.5	164.0
77.5°	128.5	143.0	164.0	183.6	183.6	178.4	170.5	156.1	143.0	131.2	124.6
80°	91.8	101.0	118.0	124.6	127.2	125.9	119.4	108.9	103.6	94.4	91.8
82.5°	59.0	65.6	73.5	80.0	83.9	81.3	80.0	74.8	66.9	64.3	61.6
85°	34.1	36.7	40.7	44.6	45.9	44.6	47.2	43.3	39.3	39.3	38.0
87.5°	14.4	15.7	18.4	18.4	19.7	19.7	18.4	19.7	19.7	18.4	17.1
90°	1.0	3.9	7.9	9.8	11.8	13.2	14.7	19.6	26.5	32.4	33.4
92.5°	14.7	20.6	28.5	33.4	41.3	46.7	52.1	78.6	115.9	149.3	151.3
95°	34.4	38.3	48.1	57.0	72.7	84.5	96.3	141.5	226.9	340.9	385.1
97.5°	51.1	57.0	67.8	80.6	98.2	111.5	124.8	182.7	301.6	485.3	627.8
100°	75.6	78.6	87.4	103.2	122.8	136.6	150.3	202.4	322.2	534.4	776.1
102.5°	98.2	100.2	109.1	124.8	145.4	159.2	172.9	220.1	323.2	515.8	781.0
105°	119.9	123.8	130.7	145.4	167.0	180.8	194.5	240.7	328.1	490.2	728.0
107.5°	143.4	146.4	153.3	167.0	188.6	202.4	216.1	261.3	338.9	476.5	678.9
110°	167.0	170.9	176.8	189.6	210.2	224.4	238.7	282.0	352.7	472.6	645.5

TEST NUMBER: P1009638

CATALOG NUMBER: S122DIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	188.6	192.6	199.4	211.2	230.9	245.6	260.3	301.6	367.4	473.5	623.9
115°	211.2	216.1	222.0	233.8	253.5	266.8	280.0	322.2	382.2	477.5	609.1
117.5°	234.8	238.7	244.6	255.4	274.1	287.8	301.6	340.9	397.9	483.4	601.3
120°	256.4	260.3	266.2	275.1	294.7	308.4	322.2	360.6	413.6	489.3	594.4
122.5°	277.0	280.0	285.9	295.7	315.4	329.6	343.9	379.2	427.4	496.1	590.4
125°	294.7	297.7	303.6	315.4	335.0	348.8	362.5	397.9	442.1	503.0	585.5
127.5°	309.5	313.4	321.3	334.0	352.7	367.0	381.2	415.6	455.9	509.9	582.6
130°	322.2	326.2	336.0	349.7	369.4	383.2	396.9	431.3	468.6	517.7	580.6
132.5°	334.0	338.9	349.7	364.5	385.1	398.8	412.6	445.0	481.4	525.6	579.6
135°	345.8	349.7	361.5	376.3	398.9	412.6	426.4	457.8	492.2	531.5	578.7
137.5°	356.6	361.5	373.3	389.0	411.6	424.4	437.2	468.6	501.0	537.4	578.7
140°	369.4	373.3	385.1	400.8	422.5	435.2	448.0	477.5	507.9	541.3	577.7
142.5°	382.2	385.1	395.9	411.6	432.3	444.1	455.9	484.3	513.8	544.3	577.7
145°	394.9	398.9	408.7	423.4	443.1	453.9	464.7	491.2	518.7	546.2	575.7
147.5°	408.7	411.6	421.5	435.2	451.9	461.8	471.6	497.1	521.7	547.2	572.8
150°	422.5	425.4	433.3	446.0	460.8	469.6	478.5	501.0	523.6	546.2	569.8
152.5°	436.2	437.2	445.0	455.9	469.6	477.4	485.3	505.0	524.6	544.3	564.9
155°	449.0	450.0	455.9	466.7	477.5	484.8	492.2	508.9	525.6	542.3	559.0
157.5°	459.8	460.8	465.7	475.5	484.3	490.7	497.1	511.9	525.6	538.4	553.1
160°	470.6	471.6	475.5	483.4	491.2	496.6	502.0	513.8	525.6	535.4	547.2
162.5°	481.4	480.4	484.3	490.2	497.1	501.0	505.0	514.8	524.6	532.5	542.3
165°	489.3	488.3	490.2	496.1	501.0	504.0	506.9	515.8	522.7	528.6	535.4
167.5°	496.1	495.2	497.1	501.0	505.0	507.0	508.9	515.8	521.7	524.6	529.5
170°	503.0	501.0	502.0	505.0	506.9	508.4	509.9	514.8	519.7	521.7	524.6
172.5°	506.9	506.0	505.0	507.9	508.9	509.9	510.9	513.8	516.8	517.7	518.7
175°	509.9	508.9	507.9	509.9	509.9	510.4	510.9	512.8	514.8	513.8	514.8
177.5°	511.9	509.9	508.9	510.9	510.9	510.9	510.9	511.9	513.8	511.9	510.9
180°	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9

TEST NUMBER: P1009638

CATALOG NUMBER: S122DIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1773.4	1774.7	1777.3	1790.4	1797.0	1798.3	1793.0	1804.8	1808.8	1804.8	1802.2
5°	1857.3	1865.2	1880.9	1898.0	1896.7	1898.0	1905.8	1913.7	1916.3	1905.8	1909.8
7.5°	1930.8	1946.5	1963.6	1989.8	1989.8	2002.9	2008.2	2014.7	2030.5	2022.6	2020.0
10°	2014.7	2035.7	2067.2	2109.2	2110.5	2123.6	2136.7	2157.7	2164.2	2159.0	2161.6
12.5°	2119.6	2160.3	2162.9	2208.8	2229.8	2232.5	2253.4	2249.5	2262.6	2262.6	2284.9
15°	2165.6	2228.5	2263.9	2308.5	2321.6	2305.9	2323.0	2341.3	2342.6	2342.6	2341.3
17.5°	2248.2	2273.1	2308.5	2332.1	2337.4	2337.4	2338.7	2346.6	2341.3	2330.8	2338.7
20°	2265.2	2275.7	2288.9	2286.2	2288.9	2275.7	2262.6	2249.5	2250.8	2244.3	2263.9
22.5°	2233.8	2231.1	2201.0	2181.3	2181.3	2155.1	2130.1	2118.3	2106.5	2110.5	2117.0
25°	2155.1	2114.4	2077.7	2048.8	2042.3	2000.3	1966.2	1955.7	1936.0	1951.8	1954.4
27.5°	2029.1	1983.2	1924.2	1899.3	1865.2	1848.1	1824.5	1793.0	1752.4	1776.0	1772.1
30°	1894.0	1825.8	1777.3	1717.0	1663.2	1659.3	1614.7	1562.2	1541.2	1541.2	1553.0
32.5°	1743.2	1652.7	1581.9	1496.6	1444.1	1421.8	1368.1	1315.6	1327.4	1288.1	1302.5
35°	1567.4	1448.1	1358.9	1276.2	1236.9	1210.7	1141.1	1112.3	1080.8	1062.4	1096.6
37.5°	1399.5	1261.8	1147.7	1057.2	1042.8	995.6	948.3	930.0	911.6	919.5	918.2
40°	1194.9	1072.9	970.6	899.8	874.9	852.6	821.1	798.8	787.0	793.6	794.9
42.5°	1010.0	907.7	831.6	781.8	760.8	745.0	729.3	710.9	707.0	707.0	712.2
45°	867.0	783.1	731.9	691.2	679.4	667.6	655.8	648.0	645.3	640.1	644.0
47.5°	752.9	686.0	654.5	624.4	611.2	608.6	598.1	594.2	588.9	587.6	588.9
50°	657.1	615.2	586.3	569.3	560.1	556.1	550.9	543.0	540.4	547.0	544.3
52.5°	590.2	550.9	535.2	518.1	512.9	507.6	499.7	501.1	499.7	497.1	497.1
55°	523.4	498.4	482.7	469.6	468.3	463.0	456.5	453.8	452.5	449.9	453.8
57.5°	469.6	449.9	435.5	423.7	418.4	418.4	411.9	406.6	406.6	405.3	406.6
60°	415.8	396.1	386.9	375.1	371.2	369.9	366.0	363.3	359.4	359.4	359.4
62.5°	366.0	350.2	339.7	329.2	330.5	324.0	318.7	316.1	316.1	317.4	317.4
65°	318.7	308.2	295.1	285.9	283.3	282.0	279.4	278.1	274.1	276.8	276.8
67.5°	275.4	261.0	253.2	249.2	245.3	244.0	241.3	238.7	237.4	236.1	238.7
70°	232.2	220.4	213.8	211.2	207.2	205.9	204.6	200.7	202.0	203.3	204.6
72.5°	192.8	182.3	181.0	173.1	173.1	173.1	167.9	170.5	169.2	166.6	169.2
75°	152.2	146.9	144.3	140.3	141.7	140.3	139.0	135.1	135.1	136.4	137.7
77.5°	120.7	115.4	114.1	110.2	107.6	110.2	107.6	106.2	106.2	107.6	107.6
80°	89.2	86.6	82.6	82.6	82.6	81.3	81.3	81.3	80.0	78.7	80.0
82.5°	59.0	59.0	57.7	56.4	57.7	55.1	56.4	56.4	56.4	56.4	56.4
85°	38.0	36.7	36.7	35.4	35.4	35.4	36.7	34.1	34.1	35.4	35.4
87.5°	17.1	17.1	17.1	18.4	17.1	17.1	17.1	18.4	17.1	17.1	17.1
90°	32.4	31.4	29.5	31.4	31.9	32.4	32.4	32.4	32.4	32.4	32.4
92.5°	126.7	99.2	84.5	73.7	69.8	65.8	64.8	60.9	61.9	59.9	61.9
95°	337.0	257.4	197.5	156.2	145.4	134.6	121.8	114.0	111.0	112.0	111.0
97.5°	632.7	526.6	420.5	321.3	291.8	262.3	224.0	204.3	193.5	187.6	193.5
100°	917.6	897.0	775.1	640.6	581.2	521.7	440.1	397.9	369.4	351.7	369.4
102.5°	1023.7	1139.6	1135.7	1046.3	982.4	918.6	828.2	748.6	711.3	685.7	711.3
105°	989.3	1193.7	1304.7	1317.5	1301.2	1285.0	1224.1	1163.2	1121.0	1107.2	1121.0
107.5°	916.6	1135.7	1300.8	1397.0	1416.6	1436.3	1435.4	1426.5	1413.7	1391.1	1413.7
110°	848.8	1056.1	1232.0	1357.7	1398.0	1438.3	1480.5	1499.2	1508.1	1507.1	1508.1

TEST NUMBER: P1009638

CATALOG NUMBER: S122DIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	801.7	983.4	1150.4	1287.0	1334.6	1382.3	1445.2	1479.6	1498.2	1505.1	1498.2
115°	764.3	926.4	1077.7	1206.4	1257.0	1307.6	1377.4	1422.6	1448.1	1457.0	1448.1
117.5°	738.8	879.3	1014.9	1134.7	1182.8	1231.0	1302.7	1350.9	1377.4	1384.3	1377.4
120°	719.1	845.9	967.7	1071.8	1116.5	1161.2	1230.0	1276.2	1304.7	1314.5	1304.7
122.5°	702.4	819.4	928.4	1025.7	1065.0	1104.3	1164.2	1209.4	1233.9	1241.8	1233.9
125°	686.7	793.8	895.0	981.5	1018.3	1055.1	1112.1	1149.5	1174.0	1181.9	1174.0
127.5°	672.0	768.3	861.6	944.1	978.5	1012.9	1063.0	1098.4	1120.0	1125.9	1120.0
130°	657.3	743.7	828.2	905.8	938.2	970.7	1018.8	1052.2	1071.8	1079.7	1071.8
132.5°	645.5	720.1	796.8	866.5	896.4	926.4	973.6	1007.0	1024.7	1031.6	1024.7
135°	634.7	698.5	763.4	828.2	855.7	883.2	925.5	957.9	975.6	979.5	975.6
137.5°	626.8	680.8	736.8	789.9	814.4	839.0	879.3	907.8	923.5	929.4	923.5
140°	619.9	664.1	711.3	756.5	778.1	799.7	831.1	856.7	871.4	877.3	871.4
142.5°	613.0	650.4	688.7	726.0	743.2	760.4	789.9	812.5	825.3	825.3	825.3
145°	607.2	637.6	670.0	700.5	714.8	729.0	752.6	769.3	779.1	782.0	779.1
147.5°	601.3	627.8	654.3	678.9	689.7	700.5	721.1	734.9	741.7	743.7	741.7
150°	593.4	617.0	638.6	659.2	668.0	676.9	691.6	703.4	709.3	710.3	709.3
152.5°	586.5	606.2	625.8	642.5	649.9	657.3	668.1	677.9	681.8	681.8	681.8
155°	577.7	596.3	612.1	626.8	632.2	637.6	648.4	655.3	659.2	657.3	659.2
157.5°	569.8	584.6	598.3	611.1	615.5	619.9	627.8	633.7	635.6	635.6	635.6
160°	561.0	573.7	584.6	595.4	598.8	602.2	609.1	614.0	615.0	615.0	615.0
162.5°	553.1	562.9	571.8	580.6	583.0	585.5	592.4	595.4	596.3	595.4	596.3
165°	544.3	552.1	559.0	565.9	567.8	569.8	573.7	577.7	577.7	576.7	577.7
167.5°	535.4	541.3	547.2	552.1	554.1	556.1	558.0	560.0	560.0	559.0	560.0
170°	528.6	533.5	536.4	540.3	541.3	542.3	543.3	546.2	545.3	543.3	545.3
172.5°	521.7	524.6	526.6	529.5	530.0	530.5	531.5	532.5	531.5	530.5	531.5
175°	515.8	518.7	519.7	520.7	521.2	521.7	521.7	522.7	521.7	519.7	521.7
177.5°	511.9	513.8	513.8	514.8	514.8	514.8	514.8	514.8	513.8	511.9	513.8
180°	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9

TEST NUMBER: P1009638

CATALOG NUMBER: S122DIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1808.8	1799.6	1791.7	1793.0	1799.6	1794.4	1781.2	1764.2	1757.6	1749.8	1757.6
5°	1917.7	1909.8	1894.0	1895.4	1891.4	1886.2	1865.2	1839.0	1839.0	1818.0	1815.3
7.5°	2025.2	2013.4	2002.9	2000.3	1985.9	1975.4	1957.0	1920.3	1905.8	1880.9	1866.5
10°	2145.9	2136.7	2124.9	2110.5	2102.6	2084.2	2054.1	2000.3	1974.1	1939.9	1915.0
12.5°	2267.9	2266.6	2240.3	2211.5	2210.2	2181.3	2160.3	2088.2	2052.8	2006.8	1947.8
15°	2345.3	2338.7	2324.3	2309.8	2313.8	2282.3	2235.1	2149.8	2126.2	2071.1	2008.2
17.5°	2343.9	2343.9	2340.0	2337.4	2333.4	2324.3	2298.0	2241.6	2203.6	2134.1	2075.1
20°	2269.2	2286.2	2290.2	2288.9	2302.0	2308.5	2307.2	2271.8	2241.6	2180.0	2119.6
22.5°	2119.6	2159.0	2176.0	2186.5	2214.1	2228.5	2262.6	2249.5	2241.6	2195.7	2144.6
25°	1980.6	1993.7	2044.9	2047.5	2085.5	2121.0	2155.1	2177.4	2206.2	2189.2	2145.9
27.5°	1800.9	1831.1	1867.8	1895.4	1903.2	1975.4	2031.8	2073.7	2139.3	2144.6	2130.1
30°	1597.6	1612.0	1672.4	1709.1	1751.1	1803.5	1884.9	1957.0	2016.0	2069.8	2088.2
32.5°	1349.7	1408.7	1444.1	1488.7	1525.5	1618.6	1718.3	1811.4	1879.6	1970.1	2009.5
35°	1122.8	1168.7	1229.0	1247.4	1314.3	1393.0	1522.8	1642.2	1745.8	1837.6	1917.7
37.5°	935.2	971.9	1036.2	1065.1	1104.4	1205.4	1314.3	1462.5	1587.1	1699.9	1799.6
40°	806.7	834.2	882.7	891.9	924.7	1016.5	1104.4	1243.5	1408.7	1560.9	1669.7
42.5°	718.8	731.9	764.7	776.5	797.5	859.1	937.8	1069.0	1222.5	1379.9	1533.3
45°	655.8	665.0	684.7	695.2	721.4	749.0	813.2	918.2	1038.8	1197.5	1362.8
47.5°	599.4	611.2	619.1	625.7	640.1	670.3	712.2	789.6	905.0	1050.6	1210.7
50°	552.2	556.1	570.6	571.9	581.1	600.7	640.1	687.3	779.1	897.2	1052.0
52.5°	505.0	508.9	518.1	527.3	531.2	547.0	573.2	612.5	680.8	773.9	911.6
55°	457.8	463.0	472.2	478.8	482.7	495.8	511.5	549.6	603.4	668.9	781.8
57.5°	410.6	422.4	425.0	428.9	435.5	449.9	464.3	486.6	528.6	588.9	671.6
60°	366.0	369.9	379.1	383.0	389.6	397.4	415.8	432.8	463.0	510.2	585.0
62.5°	320.0	329.2	333.2	337.1	342.3	351.5	363.3	381.7	407.9	446.0	505.0
65°	280.7	282.0	289.9	295.1	300.4	306.9	318.7	335.8	351.5	386.9	430.2
67.5°	242.7	245.3	247.9	253.2	259.7	266.3	276.8	285.9	305.6	329.2	363.3
70°	205.9	205.9	212.5	216.4	215.1	223.0	230.9	241.3	255.8	278.1	305.6
72.5°	173.1	171.8	177.1	178.4	181.0	186.3	191.5	202.0	209.9	226.9	247.9
75°	137.7	140.3	143.0	143.0	146.9	150.8	156.1	161.3	170.5	181.0	196.7
77.5°	108.9	108.9	111.5	112.8	116.7	115.4	120.7	125.9	132.5	141.7	153.5
80°	80.0	82.6	82.6	82.6	83.9	85.3	90.5	94.4	98.4	104.9	110.2
82.5°	56.4	56.4	59.0	59.0	59.0	61.6	61.6	63.0	65.6	69.5	73.5
85°	35.4	35.4	35.4	36.7	35.4	36.7	39.3	38.0	39.3	42.0	42.0
87.5°	17.1	17.1	17.1	17.1	17.1	18.4	17.1	18.4	19.7	19.7	19.7
90°	32.4	32.4	32.4	31.9	31.4	29.5	31.4	32.4	33.4	32.4	26.5
92.5°	60.9	64.8	65.8	69.8	73.7	84.5	99.2	126.7	151.3	149.3	115.9
95°	114.0	121.8	134.6	145.4	156.2	197.5	257.4	337.0	385.1	340.9	226.9
97.5°	204.3	224.0	262.3	291.8	321.3	420.5	526.6	632.7	627.8	485.3	301.6
100°	397.9	440.1	521.7	581.2	640.6	775.1	897.0	917.6	776.1	534.4	322.2
102.5°	748.6	828.2	918.6	982.4	1046.3	1135.7	1139.6	1023.7	781.0	515.8	323.2
105°	1163.2	1224.1	1285.0	1301.2	1317.5	1304.7	1193.7	989.3	728.0	490.2	328.1
107.5°	1426.5	1435.4	1436.3	1416.6	1397.0	1300.8	1135.7	916.6	678.9	476.5	338.9
110°	1499.2	1480.5	1438.3	1398.0	1357.7	1232.0	1056.1	848.8	645.5	472.6	352.7

TEST NUMBER: P1009638

CATALOG NUMBER: S122DIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1479.6	1445.2	1382.3	1334.6	1287.0	1150.4	983.4	801.7	623.9	473.5	367.4
115°	1422.6	1377.4	1307.6	1257.0	1206.4	1077.7	926.4	764.3	609.1	477.5	382.2
117.5°	1350.9	1302.7	1231.0	1182.8	1134.7	1014.9	879.3	738.8	601.3	483.4	397.9
120°	1276.2	1230.0	1161.2	1116.5	1071.8	967.7	845.9	719.1	594.4	489.3	413.6
122.5°	1209.4	1164.2	1104.3	1065.0	1025.7	928.4	819.4	702.4	590.4	496.1	427.4
125°	1149.5	1112.1	1055.1	1018.3	981.5	895.0	793.8	686.7	585.5	503.0	442.1
127.5°	1098.4	1063.0	1012.9	978.5	944.1	861.6	768.3	672.0	582.6	509.9	455.9
130°	1052.2	1018.8	970.7	938.2	905.8	828.2	743.7	657.3	580.6	517.7	468.6
132.5°	1007.0	973.6	926.4	896.4	866.5	796.8	720.1	645.5	579.6	525.6	481.4
135°	957.9	925.5	883.2	855.7	828.2	763.4	698.5	634.7	578.7	531.5	492.2
137.5°	907.8	879.3	839.0	814.4	789.9	736.8	680.8	626.8	578.7	537.4	501.0
140°	856.7	831.1	799.7	778.1	756.5	711.3	664.1	619.9	577.7	541.3	507.9
142.5°	812.5	789.9	760.4	743.2	726.0	688.7	650.4	613.0	577.7	544.3	513.8
145°	769.3	752.6	729.0	714.8	700.5	670.0	637.6	607.2	575.7	546.2	518.7
147.5°	734.9	721.1	700.5	689.7	678.9	654.3	627.8	601.3	572.8	547.2	521.7
150°	703.4	691.6	676.9	668.0	659.2	638.6	617.0	593.4	569.8	546.2	523.6
152.5°	677.9	668.1	657.3	649.9	642.5	625.8	606.2	586.5	564.9	544.3	524.6
155°	655.3	648.4	637.6	632.2	626.8	612.1	596.3	577.7	559.0	542.3	525.6
157.5°	633.7	627.8	619.9	615.5	611.1	598.3	584.6	569.8	553.1	538.4	525.6
160°	614.0	609.1	602.2	598.8	595.4	584.6	573.7	561.0	547.2	535.4	525.6
162.5°	595.4	592.4	585.5	583.0	580.6	571.8	562.9	553.1	542.3	532.5	524.6
165°	577.7	573.7	569.8	567.8	565.9	559.0	552.1	544.3	535.4	528.6	522.7
167.5°	560.0	558.0	556.1	554.1	552.1	547.2	541.3	535.4	529.5	524.6	521.7
170°	546.2	543.3	542.3	541.3	540.3	536.4	533.5	528.6	524.6	521.7	519.7
172.5°	532.5	531.5	530.5	530.0	529.5	526.6	524.6	521.7	518.7	517.7	516.8
175°	522.7	521.7	521.7	521.2	520.7	519.7	518.7	515.8	514.8	513.8	514.8
177.5°	514.8	514.8	514.8	514.8	514.8	513.8	513.8	511.9	510.9	511.9	513.8
180°	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9

TEST NUMBER: P1009638

CATALOG NUMBER: S122DIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1751.1	1744.5	1740.6	1743.2	1735.3	1715.7	1715.7	1722.2	1714.3	1706.5	1694.7
5°	1799.6	1786.5	1778.6	1777.3	1758.9	1727.5	1720.9	1714.3	1697.3	1678.9	1659.3
7.5°	1846.8	1823.2	1810.1	1800.9	1774.7	1734.0	1717.0	1702.5	1675.0	1647.4	1622.5
10°	1886.2	1852.1	1836.3	1821.9	1787.8	1736.6	1709.1	1682.9	1647.4	1612.0	1580.6
12.5°	1917.7	1878.3	1858.6	1837.6	1795.7	1728.8	1694.7	1652.7	1617.3	1570.1	1538.6
15°	1970.1	1888.8	1870.4	1850.8	1807.5	1715.7	1673.7	1626.5	1577.9	1515.0	1480.9
17.5°	2012.1	1903.2	1901.9	1859.9	1803.5	1710.4	1646.1	1584.5	1532.0	1469.1	1415.3
20°	2037.0	1925.5	1904.5	1861.2	1790.4	1675.0	1608.1	1539.9	1483.5	1407.4	1353.6
22.5°	2058.0	1957.0	1901.9	1849.4	1762.9	1663.2	1564.8	1500.5	1423.2	1340.5	1289.4
25°	2065.9	1963.6	1905.8	1845.5	1743.2	1629.1	1517.6	1448.1	1361.5	1286.7	1217.2
27.5°	2067.2	1962.2	1891.4	1828.5	1715.7	1584.5	1470.4	1396.9	1301.2	1214.6	1145.1
30°	2054.1	1947.8	1883.5	1815.3	1689.4	1543.8	1412.7	1331.3	1229.0	1142.5	1070.3
32.5°	2014.7	1919.0	1866.5	1791.7	1655.3	1487.4	1357.6	1267.1	1159.5	1074.3	1004.7
35°	1949.1	1883.5	1825.8	1756.3	1610.7	1435.0	1302.5	1196.2	1087.4	1006.0	940.5
37.5°	1867.8	1832.4	1778.6	1710.4	1559.6	1387.7	1240.8	1122.8	1013.9	935.2	870.9
40°	1757.6	1766.8	1714.3	1652.7	1499.2	1323.5	1160.8	1048.0	945.7	872.3	809.3
42.5°	1638.3	1676.3	1646.1	1587.1	1432.3	1252.6	1101.8	977.2	877.5	801.4	749.0
45°	1509.7	1575.3	1556.9	1513.7	1362.8	1177.9	1017.9	897.2	809.3	735.8	689.9
47.5°	1369.4	1462.5	1462.5	1431.0	1285.4	1103.1	945.7	822.4	735.8	683.4	638.8
50°	1226.4	1331.3	1348.4	1327.4	1198.9	1017.9	857.8	746.3	671.6	620.4	587.6
52.5°	1076.9	1198.9	1230.3	1219.8	1107.0	936.5	785.7	676.8	608.6	564.0	535.2
55°	933.9	1075.6	1109.7	1113.6	1008.7	847.3	705.7	609.9	544.3	514.2	489.3
57.5°	798.8	935.2	973.3	979.8	909.0	766.0	630.9	547.0	487.9	463.0	443.3
60°	683.4	797.5	847.3	861.8	800.1	671.6	561.4	480.1	435.5	411.9	393.5
62.5°	588.9	680.8	733.2	737.2	709.6	588.9	489.3	421.0	383.0	362.0	352.8
65°	497.1	579.8	611.2	627.0	604.7	510.2	422.4	366.0	335.8	317.4	308.2
67.5°	423.7	476.1	502.4	523.4	501.1	430.2	359.4	313.5	291.2	272.8	267.6
70°	347.6	390.9	410.6	431.5	411.9	358.1	306.9	265.0	245.3	230.9	224.3
72.5°	278.1	312.2	330.5	343.7	331.9	287.3	245.3	216.4	202.0	191.5	187.6
75°	220.4	244.0	254.5	263.6	258.4	224.3	198.1	174.5	161.3	152.2	149.5
77.5°	167.9	184.9	196.7	199.4	192.8	170.5	148.2	133.8	123.3	118.0	115.4
80°	119.4	129.9	136.4	140.3	133.8	124.6	108.9	98.4	89.2	82.6	81.3
82.5°	80.0	85.3	90.5	89.2	86.6	78.7	69.5	64.3	60.3	55.1	55.1
85°	45.9	47.2	49.8	51.2	49.8	44.6	39.3	36.7	34.1	30.2	30.2
87.5°	19.7	21.0	21.0	22.3	19.7	19.7	17.1	14.4	14.4	13.1	11.8
90°	19.6	14.7	13.2	11.8	9.8	7.9	3.9	1.0	3.9	7.9	9.8
92.5°	78.6	52.1	46.7	41.3	33.4	28.5	20.6	14.7	20.6	28.5	33.4
95°	141.5	96.3	84.5	72.7	57.0	48.1	38.3	34.4	38.3	48.1	57.0
97.5°	182.7	124.8	111.5	98.2	80.6	67.8	57.0	51.1	57.0	67.8	80.6
100°	202.4	150.3	136.6	122.8	103.2	87.4	78.6	75.6	78.6	87.4	103.2
102.5°	220.1	172.9	159.2	145.4	124.8	109.1	100.2	98.2	100.2	109.1	124.8
105°	240.7	194.5	180.8	167.0	145.4	130.7	123.8	119.9	123.8	130.7	145.4
107.5°	261.3	216.1	202.4	188.6	167.0	153.3	146.4	143.4	146.4	153.3	167.0
110°	282.0	238.7	224.4	210.2	189.6	176.8	170.9	167.0	170.9	176.8	189.6

TEST NUMBER: P1009638

CATALOG NUMBER: S122DIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	301.6	260.3	245.6	230.9	211.2	199.4	192.6	188.6	192.6	199.4	211.2
115°	322.2	280.0	266.8	253.5	233.8	222.0	216.1	211.2	216.1	222.0	233.8
117.5°	340.9	301.6	287.8	274.1	255.4	244.6	238.7	234.8	238.7	244.6	255.4
120°	360.6	322.2	308.4	294.7	275.1	266.2	260.3	256.4	260.3	266.2	275.1
122.5°	379.2	343.9	329.6	315.4	295.7	285.9	280.0	277.0	280.0	285.9	295.7
125°	397.9	362.5	348.8	335.0	315.4	303.6	297.7	294.7	297.7	303.6	315.4
127.5°	415.6	381.2	367.0	352.7	334.0	321.3	313.4	309.5	313.4	321.3	334.0
130°	431.3	396.9	383.2	369.4	349.7	336.0	326.2	322.2	326.2	336.0	349.7
132.5°	445.0	412.6	398.8	385.1	364.5	349.7	338.9	334.0	338.9	349.7	364.5
135°	457.8	426.4	412.6	398.9	376.3	361.5	349.7	345.8	349.7	361.5	376.3
137.5°	468.6	437.2	424.4	411.6	389.0	373.3	361.5	356.6	361.5	373.3	389.0
140°	477.5	448.0	435.2	422.5	400.8	385.1	373.3	369.4	373.3	385.1	400.8
142.5°	484.3	455.9	444.1	432.3	411.6	395.9	385.1	382.2	385.1	395.9	411.6
145°	491.2	464.7	453.9	443.1	423.4	408.7	398.9	394.9	398.9	408.7	423.4
147.5°	497.1	471.6	461.8	451.9	435.2	421.5	411.6	408.7	411.6	421.5	435.2
150°	501.0	478.5	469.6	460.8	446.0	433.3	425.4	422.5	425.4	433.3	446.0
152.5°	505.0	485.3	477.4	469.6	455.9	445.0	437.2	436.2	437.2	445.0	455.9
155°	508.9	492.2	484.8	477.5	466.7	455.9	450.0	449.0	450.0	455.9	466.7
157.5°	511.9	497.1	490.7	484.3	475.5	465.7	460.8	459.8	460.8	465.7	475.5
160°	513.8	502.0	496.6	491.2	483.4	475.5	471.6	470.6	471.6	475.5	483.4
162.5°	514.8	505.0	501.0	497.1	490.2	484.3	480.4	481.4	480.4	484.3	490.2
165°	515.8	506.9	504.0	501.0	496.1	490.2	488.3	489.3	488.3	490.2	496.1
167.5°	515.8	508.9	507.0	505.0	501.0	497.1	495.2	496.1	495.2	497.1	501.0
170°	514.8	509.9	508.4	506.9	505.0	502.0	501.0	503.0	501.0	502.0	505.0
172.5°	513.8	510.9	509.9	508.9	507.9	505.0	506.0	506.9	506.0	505.0	507.9
175°	512.8	510.9	510.4	509.9	509.9	507.9	508.9	509.9	508.9	507.9	509.9
177.5°	511.9	510.9	510.9	510.9	510.9	508.9	509.9	511.9	509.9	508.9	510.9
180°	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9

TEST NUMBER: P1009638

CATALOG NUMBER: S122DIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1688.1	1694.7	1693.4	1680.2	1665.8	1654.0	1631.7	1634.3	1626.5	1627.8	1635.6
5°	1646.1	1646.1	1640.9	1622.5	1598.9	1585.8	1560.9	1554.3	1538.6	1537.3	1536.0
7.5°	1601.5	1595.0	1588.4	1562.2	1533.3	1512.3	1478.2	1470.4	1454.6	1444.1	1438.9
10°	1549.1	1539.9	1526.8	1496.6	1461.2	1435.0	1399.5	1389.1	1358.9	1345.8	1337.9
12.5°	1491.4	1486.1	1465.1	1440.2	1382.5	1353.6	1302.5	1313.0	1282.8	1256.6	1252.6
15°	1433.6	1414.0	1402.2	1361.5	1292.0	1278.9	1238.2	1217.2	1189.7	1168.7	1168.7
17.5°	1377.2	1347.1	1320.8	1277.6	1226.4	1189.7	1159.5	1149.0	1114.9	1093.9	1090.0
20°	1302.5	1268.4	1261.8	1200.2	1164.8	1124.1	1095.2	1069.0	1044.1	1034.9	1028.3
22.5°	1231.7	1192.3	1181.8	1129.3	1093.9	1053.3	1024.4	1006.0	987.7	981.1	969.3
25°	1155.6	1132.0	1116.2	1059.8	1020.5	982.4	962.8	949.6	932.6	931.3	923.4
27.5°	1082.1	1059.8	1044.1	990.3	961.4	926.0	910.3	895.9	886.7	882.7	878.8
30°	1019.2	994.2	975.9	936.5	901.1	872.3	859.1	850.0	844.7	838.2	836.8
32.5°	949.6	935.2	910.3	880.1	852.6	825.0	817.2	810.6	802.7	800.1	798.8
35°	890.6	870.9	855.2	821.1	809.3	785.7	776.5	771.3	760.8	758.1	755.5
37.5°	832.9	814.5	797.5	776.5	754.2	741.1	735.8	728.0	722.7	724.0	721.4
40°	775.2	760.8	747.6	725.3	712.2	705.7	695.2	687.3	684.7	686.0	684.7
42.5°	718.8	705.7	697.8	680.8	667.6	661.1	654.5	646.6	650.6	650.6	654.5
45°	667.6	655.8	650.6	637.5	629.6	619.1	612.5	611.2	616.5	615.2	615.2
47.5°	615.2	611.2	604.7	592.9	582.4	575.8	574.5	574.5	579.8	582.4	581.1
50°	574.5	566.6	558.8	549.6	541.7	539.1	535.2	537.8	543.0	543.0	545.7
52.5°	523.4	518.1	515.5	507.6	502.4	502.4	502.4	503.7	507.6	511.5	510.2
55°	478.8	474.8	472.2	468.3	461.7	463.0	461.7	464.3	468.3	472.2	474.8
57.5°	431.5	430.2	427.6	421.0	421.0	419.7	423.7	425.0	431.5	434.2	438.1
60°	389.6	385.6	385.6	380.4	380.4	380.4	384.3	388.3	393.5	394.8	397.4
62.5°	345.0	345.0	343.7	339.7	339.7	343.7	345.0	350.2	352.8	352.8	356.8
65°	303.0	301.7	300.4	301.7	303.0	303.0	306.9	309.6	312.2	313.5	314.8
67.5°	261.0	259.7	262.3	261.0	263.6	268.9	267.6	271.5	275.4	275.4	276.8
70°	221.7	224.3	223.0	225.6	224.3	226.9	230.9	232.2	232.2	233.5	237.4
72.5°	184.9	184.9	184.9	183.6	184.9	187.6	190.2	191.5	194.1	195.4	199.4
75°	149.5	149.5	146.9	149.5	149.5	152.2	154.8	154.8	154.8	157.4	161.3
77.5°	112.8	114.1	112.8	115.4	115.4	116.7	119.4	118.0	120.7	122.0	123.3
80°	82.6	81.3	81.3	81.3	82.6	82.6	85.3	86.6	86.6	90.5	87.9
82.5°	52.5	53.8	52.5	53.8	53.8	55.1	53.8	55.1	56.4	59.0	57.7
85°	30.2	28.9	28.9	30.2	28.9	28.9	30.2	28.9	30.2	28.9	30.2
87.5°	11.8	10.5	10.5	10.5	10.5	9.2	9.2	7.9	7.9	7.9	6.6
90°	11.8	13.2	14.7	19.6	26.5	32.4	33.4	32.4	31.4	29.5	31.4
92.5°	41.3	46.7	52.1	78.6	115.9	149.3	151.3	126.7	99.2	84.5	73.7
95°	72.7	84.5	96.3	141.5	226.9	340.9	385.1	337.0	257.4	197.5	156.2
97.5°	98.2	111.5	124.8	182.7	301.6	485.3	627.8	632.7	526.6	420.5	321.3
100°	122.8	136.6	150.3	202.4	322.2	534.4	776.1	917.6	897.0	775.1	640.6
102.5°	145.4	159.2	172.9	220.1	323.2	515.8	781.0	1023.7	1139.6	1135.7	1046.3
105°	167.0	180.8	194.5	240.7	328.1	490.2	728.0	989.3	1193.7	1304.7	1317.5
107.5°	188.6	202.4	216.1	261.3	338.9	476.5	678.9	916.6	1135.7	1300.8	1397.0
110°	210.2	224.4	238.7	282.0	352.7	472.6	645.5	848.8	1056.1	1232.0	1357.7

TEST NUMBER: P1009638

CATALOG NUMBER: S122DIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	230.9	245.6	260.3	301.6	367.4	473.5	623.9	801.7	983.4	1150.4	1287.0
115°	253.5	266.8	280.0	322.2	382.2	477.5	609.1	764.3	926.4	1077.7	1206.4
117.5°	274.1	287.8	301.6	340.9	397.9	483.4	601.3	738.8	879.3	1014.9	1134.7
120°	294.7	308.4	322.2	360.6	413.6	489.3	594.4	719.1	845.9	967.7	1071.8
122.5°	315.4	329.6	343.9	379.2	427.4	496.1	590.4	702.4	819.4	928.4	1025.7
125°	335.0	348.8	362.5	397.9	442.1	503.0	585.5	686.7	793.8	895.0	981.5
127.5°	352.7	367.0	381.2	415.6	455.9	509.9	582.6	672.0	768.3	861.6	944.1
130°	369.4	383.2	396.9	431.3	468.6	517.7	580.6	657.3	743.7	828.2	905.8
132.5°	385.1	398.8	412.6	445.0	481.4	525.6	579.6	645.5	720.1	796.8	866.5
135°	398.9	412.6	426.4	457.8	492.2	531.5	578.7	634.7	698.5	763.4	828.2
137.5°	411.6	424.4	437.2	468.6	501.0	537.4	578.7	626.8	680.8	736.8	789.9
140°	422.5	435.2	448.0	477.5	507.9	541.3	577.7	619.9	664.1	711.3	756.5
142.5°	432.3	444.1	455.9	484.3	513.8	544.3	577.7	613.0	650.4	688.7	726.0
145°	443.1	453.9	464.7	491.2	518.7	546.2	575.7	607.2	637.6	670.0	700.5
147.5°	451.9	461.8	471.6	497.1	521.7	547.2	572.8	601.3	627.8	654.3	678.9
150°	460.8	469.6	478.5	501.0	523.6	546.2	569.8	593.4	617.0	638.6	659.2
152.5°	469.6	477.4	485.3	505.0	524.6	544.3	564.9	586.5	606.2	625.8	642.5
155°	477.5	484.8	492.2	508.9	525.6	542.3	559.0	577.7	596.3	612.1	626.8
157.5°	484.3	490.7	497.1	511.9	525.6	538.4	553.1	569.8	584.6	598.3	611.1
160°	491.2	496.6	502.0	513.8	525.6	535.4	547.2	561.0	573.7	584.6	595.4
162.5°	497.1	501.0	505.0	514.8	524.6	532.5	542.3	553.1	562.9	571.8	580.6
165°	501.0	504.0	506.9	515.8	522.7	528.6	535.4	544.3	552.1	559.0	565.9
167.5°	505.0	507.0	508.9	515.8	521.7	524.6	529.5	535.4	541.3	547.2	552.1
170°	506.9	508.4	509.9	514.8	519.7	521.7	524.6	528.6	533.5	536.4	540.3
172.5°	508.9	509.9	510.9	513.8	516.8	517.7	518.7	521.7	524.6	526.6	529.5
175°	509.9	510.4	510.9	512.8	514.8	513.8	514.8	515.8	518.7	519.7	520.7
177.5°	510.9	510.9	510.9	511.9	513.8	511.9	510.9	511.9	513.8	513.8	514.8
180°	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9

TEST NUMBER: P1009638

CATALOG NUMBER: S122DIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1626.5	1630.4	1621.2	1618.6	1621.2	1612.0	1614.7	1617.3	1617.3	1621.2	1623.8
5°	1532.0	1526.8	1517.6	1515.0	1512.3	1516.3	1513.7	1517.6	1518.9	1528.1	1529.4
7.5°	1438.9	1431.0	1423.2	1415.3	1412.7	1406.1	1412.7	1412.7	1421.8	1419.2	1425.8
10°	1328.7	1327.4	1316.9	1313.0	1307.7	1297.2	1311.7	1307.7	1314.3	1326.1	1328.7
12.5°	1247.4	1233.0	1239.5	1221.2	1227.7	1217.2	1218.5	1218.5	1229.0	1230.3	1227.7
15°	1170.0	1158.2	1141.1	1133.3	1129.3	1124.1	1141.1	1142.5	1134.6	1153.0	1146.4
17.5°	1091.3	1091.3	1075.6	1071.6	1061.1	1066.4	1063.8	1065.1	1062.4	1075.6	1082.1
20°	1023.1	1016.5	1011.3	1012.6	999.5	996.9	994.2	996.9	1006.0	1015.2	1017.9
22.5°	968.0	964.1	951.0	953.6	943.1	947.0	944.4	951.0	952.3	952.3	961.4
25°	915.5	910.3	911.6	906.4	902.4	902.4	898.5	902.4	907.7	910.3	911.6
27.5°	876.2	872.3	865.7	861.8	864.4	857.8	863.1	867.0	867.0	864.4	867.0
30°	829.0	831.6	831.6	818.5	823.7	821.1	825.0	827.7	827.7	829.0	826.3
32.5°	797.5	789.6	788.3	787.0	787.0	781.8	781.8	785.7	787.0	788.3	792.2
35°	755.5	755.5	749.0	752.9	747.6	749.0	747.6	749.0	751.6	747.6	751.6
37.5°	717.5	718.8	716.2	718.8	720.1	717.5	714.9	720.1	717.5	717.5	714.9
40°	684.7	683.4	684.7	684.7	684.7	686.0	683.4	683.4	683.4	680.8	678.1
42.5°	657.1	649.3	651.9	653.2	649.3	649.3	650.6	649.3	653.2	645.3	645.3
45°	617.8	615.2	616.5	616.5	619.1	615.2	617.8	619.1	615.2	613.9	611.2
47.5°	582.4	585.0	582.4	585.0	585.0	587.6	582.4	583.7	585.0	579.8	575.8
50°	547.0	547.0	550.9	549.6	550.9	548.3	548.3	547.0	548.3	545.7	541.7
52.5°	514.2	510.2	516.8	515.5	514.2	512.9	511.5	512.9	510.2	507.6	507.6
55°	473.5	473.5	477.4	478.8	478.8	476.1	473.5	474.8	473.5	472.2	470.9
57.5°	440.7	435.5	438.1	439.4	439.4	435.5	438.1	435.5	435.5	436.8	432.8
60°	398.7	398.7	396.1	400.1	400.1	397.4	397.4	398.7	396.1	394.8	393.5
62.5°	354.1	355.5	359.4	360.7	362.0	359.4	356.8	358.1	358.1	354.1	355.5
65°	316.1	318.7	324.0	322.7	320.0	321.4	318.7	320.0	316.1	317.4	313.5
67.5°	279.4	278.1	279.4	279.4	282.0	280.7	278.1	278.1	276.8	280.7	276.8
70°	240.0	240.0	240.0	240.0	241.3	242.7	240.0	237.4	238.7	236.1	234.8
72.5°	199.4	200.7	199.4	202.0	198.1	200.7	200.7	199.4	198.1	198.1	198.1
75°	161.3	164.0	160.0	161.3	160.0	162.6	161.3	161.3	158.7	157.4	158.7
77.5°	123.3	124.6	122.0	123.3	122.0	123.3	123.3	122.0	122.0	122.0	122.0
80°	87.9	89.2	87.9	86.6	85.3	87.9	85.3	86.6	87.9	86.6	89.2
82.5°	56.4	56.4	55.1	56.4	53.8	53.8	55.1	55.1	53.8	56.4	53.8
85°	27.5	27.5	30.2	27.5	26.2	26.2	26.2	27.5	26.2	28.9	27.5
87.5°	6.6	5.2	6.6	6.6	5.2	5.2	6.6	5.2	6.6	7.9	5.2
90°	31.9	32.4	32.4	32.4	32.4	32.4	32.4	32.4	32.4	32.4	31.9
92.5°	69.8	65.8	64.8	60.9	61.9	59.9	61.9	60.9	64.8	65.8	69.8
95°	145.4	134.6	121.8	114.0	111.0	112.0	111.0	114.0	121.8	134.6	145.4
97.5°	291.8	262.3	224.0	204.3	193.5	187.6	193.5	204.3	224.0	262.3	291.8
100°	581.2	521.7	440.1	397.9	369.4	351.7	369.4	397.9	440.1	521.7	581.2
102.5°	982.4	918.6	828.2	748.6	711.3	685.7	711.3	748.6	828.2	918.6	982.4
105°	1301.2	1285.0	1224.1	1163.2	1121.0	1107.2	1121.0	1163.2	1224.1	1285.0	1301.2
107.5°	1416.6	1436.3	1435.4	1426.5	1413.7	1391.1	1413.7	1426.5	1435.4	1436.3	1416.6
110°	1398.0	1438.3	1480.5	1499.2	1508.1	1507.1	1508.1	1499.2	1480.5	1438.3	1398.0

TEST NUMBER: P1009638

CATALOG NUMBER: S122DIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1334.6	1382.3	1445.2	1479.6	1498.2	1505.1	1498.2	1479.6	1445.2	1382.3	1334.6
115°	1257.0	1307.6	1377.4	1422.6	1448.1	1457.0	1448.1	1422.6	1377.4	1307.6	1257.0
117.5°	1182.8	1231.0	1302.7	1350.9	1377.4	1384.3	1377.4	1350.9	1302.7	1231.0	1182.8
120°	1116.5	1161.2	1230.0	1276.2	1304.7	1314.5	1304.7	1276.2	1230.0	1161.2	1116.5
122.5°	1065.0	1104.3	1164.2	1209.4	1233.9	1241.8	1233.9	1209.4	1164.2	1104.3	1065.0
125°	1018.3	1055.1	1112.1	1149.5	1174.0	1181.9	1174.0	1149.5	1112.1	1055.1	1018.3
127.5°	978.5	1012.9	1063.0	1098.4	1120.0	1125.9	1120.0	1098.4	1063.0	1012.9	978.5
130°	938.2	970.7	1018.8	1052.2	1071.8	1079.7	1071.8	1052.2	1018.8	970.7	938.2
132.5°	896.4	926.4	973.6	1007.0	1024.7	1031.6	1024.7	1007.0	973.6	926.4	896.4
135°	855.7	883.2	925.5	957.9	975.6	979.5	975.6	957.9	925.5	883.2	855.7
137.5°	814.4	839.0	879.3	907.8	923.5	929.4	923.5	907.8	879.3	839.0	814.4
140°	778.1	799.7	831.1	856.7	871.4	877.3	871.4	856.7	831.1	799.7	778.1
142.5°	743.2	760.4	789.9	812.5	825.3	825.3	825.3	812.5	789.9	760.4	743.2
145°	714.8	729.0	752.6	769.3	779.1	782.0	779.1	769.3	752.6	729.0	714.8
147.5°	689.7	700.5	721.1	734.9	741.7	743.7	741.7	734.9	721.1	700.5	689.7
150°	668.0	676.9	691.6	703.4	709.3	710.3	709.3	703.4	691.6	676.9	668.0
152.5°	649.9	657.3	668.1	677.9	681.8	681.8	681.8	677.9	668.1	657.3	649.9
155°	632.2	637.6	648.4	655.3	659.2	657.3	659.2	655.3	648.4	637.6	632.2
157.5°	615.5	619.9	627.8	633.7	635.6	635.6	635.6	633.7	627.8	619.9	615.5
160°	598.8	602.2	609.1	614.0	615.0	615.0	615.0	614.0	609.1	602.2	598.8
162.5°	583.0	585.5	592.4	595.4	596.3	595.4	596.3	595.4	592.4	585.5	583.0
165°	567.8	569.8	573.7	577.7	577.7	576.7	577.7	577.7	573.7	569.8	567.8
167.5°	554.1	556.1	558.0	560.0	560.0	559.0	560.0	560.0	558.0	556.1	554.1
170°	541.3	542.3	543.3	546.2	545.3	543.3	545.3	546.2	543.3	542.3	541.3
172.5°	530.0	530.5	531.5	532.5	531.5	530.5	531.5	532.5	531.5	530.5	530.0
175°	521.2	521.7	521.7	522.7	521.7	519.7	521.7	522.7	521.7	521.7	521.2
177.5°	514.8	514.8	514.8	514.8	513.8	511.9	513.8	514.8	514.8	514.8	514.8
180°	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9

TEST NUMBER: P1009638

CATALOG NUMBER: S122DIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1619.9	1630.4	1626.5	1612.0	1629.1	1629.1	1640.9	1640.9	1655.3	1660.6	1668.4
5°	1528.1	1536.0	1542.5	1536.0	1547.8	1566.1	1576.6	1585.8	1605.5	1613.3	1625.2
7.5°	1429.7	1444.1	1450.7	1450.7	1470.4	1491.4	1512.3	1525.5	1553.0	1563.5	1575.3
10°	1334.0	1351.0	1364.1	1362.8	1395.6	1408.7	1435.0	1465.1	1492.7	1508.4	1525.5
12.5°	1233.0	1242.1	1260.5	1286.7	1294.6	1318.2	1348.4	1386.4	1436.3	1450.7	1475.6
15°	1149.0	1173.9	1188.4	1200.2	1218.5	1240.8	1273.6	1310.4	1360.2	1391.7	1417.9
17.5°	1078.2	1111.0	1120.2	1117.5	1141.1	1175.2	1213.3	1240.8	1285.4	1323.5	1348.4
20°	1020.5	1033.6	1049.3	1055.9	1074.3	1111.0	1147.7	1179.2	1215.9	1246.1	1274.9
22.5°	962.8	973.3	986.4	998.2	1012.6	1033.6	1069.0	1108.4	1143.8	1172.6	1205.4
25°	915.5	922.1	933.9	943.1	958.8	973.3	998.2	1041.5	1083.4	1100.5	1129.3
27.5°	869.6	874.9	882.7	893.2	901.1	915.5	937.8	973.3	1016.5	1033.6	1072.9
30°	829.0	832.9	840.8	846.0	850.0	867.0	884.1	911.6	944.4	968.0	996.9
32.5°	790.9	794.9	802.7	804.0	809.3	818.5	834.2	859.1	888.0	907.7	932.6
35°	749.0	751.6	759.5	762.1	766.0	773.9	785.7	804.0	830.3	844.7	867.0
37.5°	716.2	714.9	720.1	724.0	729.3	733.2	737.2	755.5	775.2	788.3	805.4
40°	680.8	678.1	679.4	684.7	687.3	692.6	692.6	710.9	724.0	734.5	747.6
42.5°	645.3	644.0	641.4	644.0	646.6	648.0	649.3	662.4	675.5	684.7	699.1
45°	609.9	608.6	606.0	607.3	607.3	609.9	613.9	619.1	628.3	636.2	644.0
47.5°	577.1	574.5	570.6	569.3	571.9	571.9	571.9	577.1	586.3	588.9	596.8
50°	543.0	539.1	533.8	531.2	531.2	529.9	532.5	533.8	541.7	544.3	550.9
52.5°	506.3	503.7	498.4	493.2	494.5	491.9	493.2	494.5	497.1	501.1	505.0
55°	469.6	464.3	460.4	459.1	455.1	455.1	451.2	456.5	455.1	456.5	461.7
57.5°	434.2	428.9	422.4	419.7	415.8	414.5	411.9	410.6	411.9	415.8	419.7
60°	392.2	389.6	385.6	381.7	379.1	375.1	372.5	372.5	371.2	371.2	372.5
62.5°	351.5	350.2	345.0	343.7	341.0	338.4	334.5	331.9	331.9	334.5	335.8
65°	312.2	310.9	306.9	305.6	299.1	296.4	295.1	293.8	291.2	291.2	291.2
67.5°	275.4	271.5	271.5	265.0	259.7	257.1	254.5	253.2	253.2	253.2	254.5
70°	234.8	234.8	230.9	226.9	221.7	223.0	219.0	215.1	215.1	212.5	213.8
72.5°	195.4	194.1	190.2	188.9	184.9	181.0	178.4	181.0	177.1	175.8	177.1
75°	157.4	156.1	153.5	150.8	152.2	148.2	144.3	143.0	143.0	140.3	140.3
77.5°	120.7	123.3	118.0	116.7	114.1	111.5	110.2	108.9	108.9	108.9	111.5
80°	83.9	85.3	85.3	82.6	83.9	80.0	80.0	80.0	76.1	77.4	78.7
82.5°	53.8	53.8	52.5	53.8	52.5	52.5	51.2	51.2	49.8	49.8	51.2
85°	30.2	28.9	27.5	30.2	28.9	28.9	27.5	27.5	27.5	27.5	27.5
87.5°	6.6	7.9	7.9	7.9	7.9	9.2	9.2	9.2	10.5	10.5	10.5
90°	31.4	29.5	31.4	32.4	33.4	32.4	26.5	19.6	14.7	13.2	11.8
92.5°	73.7	84.5	99.2	126.7	151.3	149.3	115.9	78.6	52.1	46.7	41.3
95°	156.2	197.5	257.4	337.0	385.1	340.9	226.9	141.5	96.3	84.5	72.7
97.5°	321.3	420.5	526.6	632.7	627.8	485.3	301.6	182.7	124.8	111.5	98.2
100°	640.6	775.1	897.0	917.6	776.1	534.4	322.2	202.4	150.3	136.6	122.8
102.5°	1046.3	1135.7	1139.6	1023.7	781.0	515.8	323.2	220.1	172.9	159.2	145.4
105°	1317.5	1304.7	1193.7	989.3	728.0	490.2	328.1	240.7	194.5	180.8	167.0
107.5°	1397.0	1300.8	1135.7	916.6	678.9	476.5	338.9	261.3	216.1	202.4	188.6
110°	1357.7	1232.0	1056.1	848.8	645.5	472.6	352.7	282.0	238.7	224.4	210.2

TEST NUMBER: P1009638

CATALOG NUMBER: S122DIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1287.0	1150.4	983.4	801.7	623.9	473.5	367.4	301.6	260.3	245.6	230.9
115°	1206.4	1077.7	926.4	764.3	609.1	477.5	382.2	322.2	280.0	266.8	253.5
117.5°	1134.7	1014.9	879.3	738.8	601.3	483.4	397.9	340.9	301.6	287.8	274.1
120°	1071.8	967.7	845.9	719.1	594.4	489.3	413.6	360.6	322.2	308.4	294.7
122.5°	1025.7	928.4	819.4	702.4	590.4	496.1	427.4	379.2	343.9	329.6	315.4
125°	981.5	895.0	793.8	686.7	585.5	503.0	442.1	397.9	362.5	348.8	335.0
127.5°	944.1	861.6	768.3	672.0	582.6	509.9	455.9	415.6	381.2	367.0	352.7
130°	905.8	828.2	743.7	657.3	580.6	517.7	468.6	431.3	396.9	383.2	369.4
132.5°	866.5	796.8	720.1	645.5	579.6	525.6	481.4	445.0	412.6	398.8	385.1
135°	828.2	763.4	698.5	634.7	578.7	531.5	492.2	457.8	426.4	412.6	398.9
137.5°	789.9	736.8	680.8	626.8	578.7	537.4	501.0	468.6	437.2	424.4	411.6
140°	756.5	711.3	664.1	619.9	577.7	541.3	507.9	477.5	448.0	435.2	422.5
142.5°	726.0	688.7	650.4	613.0	577.7	544.3	513.8	484.3	455.9	444.1	432.3
145°	700.5	670.0	637.6	607.2	575.7	546.2	518.7	491.2	464.7	453.9	443.1
147.5°	678.9	654.3	627.8	601.3	572.8	547.2	521.7	497.1	471.6	461.8	451.9
150°	659.2	638.6	617.0	593.4	569.8	546.2	523.6	501.0	478.5	469.6	460.8
152.5°	642.5	625.8	606.2	586.5	564.9	544.3	524.6	505.0	485.3	477.4	469.6
155°	626.8	612.1	596.3	577.7	559.0	542.3	525.6	508.9	492.2	484.8	477.5
157.5°	611.1	598.3	584.6	569.8	553.1	538.4	525.6	511.9	497.1	490.7	484.3
160°	595.4	584.6	573.7	561.0	547.2	535.4	525.6	513.8	502.0	496.6	491.2
162.5°	580.6	571.8	562.9	553.1	542.3	532.5	524.6	514.8	505.0	501.0	497.1
165°	565.9	559.0	552.1	544.3	535.4	528.6	522.7	515.8	506.9	504.0	501.0
167.5°	552.1	547.2	541.3	535.4	529.5	524.6	521.7	515.8	508.9	507.0	505.0
170°	540.3	536.4	533.5	528.6	524.6	521.7	519.7	514.8	509.9	508.4	506.9
172.5°	529.5	526.6	524.6	521.7	518.7	517.7	516.8	513.8	510.9	509.9	508.9
175°	520.7	519.7	518.7	515.8	514.8	513.8	514.8	512.8	510.9	510.4	509.9
177.5°	514.8	513.8	513.8	511.9	510.9	511.9	513.8	511.9	510.9	510.9	510.9
180°	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9	510.9

TEST NUMBER: P1009638

CATALOG NUMBER: S122DIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1706.5	1706.5	1706.5	1706.5
2.5°	1675.0	1675.0	1694.7	1715.7
5°	1638.3	1647.4	1678.9	1707.8
7.5°	1602.9	1618.6	1657.9	1694.7
10°	1559.6	1580.6	1629.1	1672.4
12.5°	1517.6	1537.3	1593.7	1642.2
15°	1458.6	1483.5	1543.8	1604.2
17.5°	1399.5	1424.5	1497.9	1568.7
20°	1330.0	1362.8	1445.5	1539.9
22.5°	1265.8	1306.4	1398.2	1474.3
25°	1194.9	1257.9	1343.1	1441.5
27.5°	1132.0	1194.9	1281.5	1381.2
30°	1061.1	1125.4	1214.6	1306.4
32.5°	992.9	1052.0	1138.5	1251.3
35°	922.1	978.5	1062.4	1176.6
37.5°	857.8	912.9	1004.7	1109.7
40°	794.9	852.6	931.3	1036.2
42.5°	735.8	787.0	857.8	962.8
45°	682.1	718.8	784.4	882.7
47.5°	625.7	658.5	718.8	817.2
50°	573.2	600.7	653.2	745.0
52.5°	522.0	545.7	594.2	667.6
55°	476.1	498.4	533.8	606.0
57.5°	428.9	446.0	480.1	537.8
60°	383.0	398.7	426.3	473.5
62.5°	337.1	350.2	376.4	414.5
65°	296.4	306.9	326.6	359.4
67.5°	257.1	263.6	279.4	305.6
70°	219.0	224.3	237.4	258.4
72.5°	178.4	183.6	198.1	212.5
75°	144.3	145.6	156.1	167.9
77.5°	112.8	111.5	119.4	128.5
80°	77.4	81.3	87.9	91.8
82.5°	52.5	53.8	56.4	59.0
85°	28.9	30.2	30.2	34.1
87.5°	11.8	13.1	13.1	14.4
90°	9.8	7.9	3.9	1.0
92.5°	33.4	28.5	20.6	14.7
95°	57.0	48.1	38.3	34.4
97.5°	80.6	67.8	57.0	51.1
100°	103.2	87.4	78.6	75.6
102.5°	124.8	109.1	100.2	98.2
105°	145.4	130.7	123.8	119.9
107.5°	167.0	153.3	146.4	143.4
110°	189.6	176.8	170.9	167.0

TEST NUMBER: P1009638

CATALOG NUMBER: S122DIP-B865D925UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	211.2	199.4	192.6	188.6
115°	233.8	222.0	216.1	211.2
117.5°	255.4	244.6	238.7	234.8
120°	275.1	266.2	260.3	256.4
122.5°	295.7	285.9	280.0	277.0
125°	315.4	303.6	297.7	294.7
127.5°	334.0	321.3	313.4	309.5
130°	349.7	336.0	326.2	322.2
132.5°	364.5	349.7	338.9	334.0
135°	376.3	361.5	349.7	345.8
137.5°	389.0	373.3	361.5	356.6
140°	400.8	385.1	373.3	369.4
142.5°	411.6	395.9	385.1	382.2
145°	423.4	408.7	398.9	394.9
147.5°	435.2	421.5	411.6	408.7
150°	446.0	433.3	425.4	422.5
152.5°	455.9	445.0	437.2	436.2
155°	466.7	455.9	450.0	449.0
157.5°	475.5	465.7	460.8	459.8
160°	483.4	475.5	471.6	470.6
162.5°	490.2	484.3	480.4	481.4
165°	496.1	490.2	488.3	489.3
167.5°	501.0	497.1	495.2	496.1
170°	505.0	502.0	501.0	503.0
172.5°	507.9	505.0	506.0	506.9
175°	509.9	507.9	508.9	509.9
177.5°	510.9	508.9	509.9	511.9
180°	510.9	510.9	510.9	510.9

(END OF REPORT)