

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009820

Luminaire Tested: S122RDIP-B290D1080UB40-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009820
REPORT IS A COMBINATION OF REPORTS P988047 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B290D1080UB40-4F0-XX-W2A-A1
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4921.0 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009820

CATALOG NUMBER: S122RDIP-B290D1080UB40-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1009820

CATALOG NUMBER: S122RDIP-B290D1080UB40-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	31	31	22
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	26	26	26	19
2	84	77	71	67	74	69	64	60	53	50	47	38	36	35	25	24	23	23	23	17
3	77	68	61	56	68	61	55	50	47	43	40	34	32	30	22	21	20	20	20	15
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	20	19	17	17	17	13
5	65	54	46	41	57	48	42	37	37	33	30	28	25	22	18	17	15	15	15	12
6	59	48	41	35	53	43	37	32	34	29	26	25	22	20	17	15	14	14	14	10
7	55	44	36	31	49	39	33	28	31	26	23	23	20	18	15	14	12	12	12	9
8	51	39	32	27	45	35	29	25	28	23	20	21	18	16	14	12	11	11	11	9
9	47	36	29	24	42	32	26	22	26	21	18	19	16	14	13	11	10	10	10	8
10	44	33	26	22	39	30	24	20	24	19	16	18	15	13	12	11	9	9	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10012	10012	10012	10012
5°	10035	10634	10070	8496
10°	9925	11240	9995	7015
15°	9709	11243	9873	5270
20°	9450	9293	9655	4348
25°	9136	5807	9333	3699
30°	8735	3718	8973	3185
35°	8248	2858	8514	2725
40°	7703	2402	8033	2384
45°	7122	2044	7421	2001
50°	6526	1737	6832	1731
55°	5867	1510	6185	1489
60°	5283	1151	5562	1137
65°	4735	866	5016	982
70°	4131	692	4452	801
75°	3491	530	3810	605
80°	2770	359	2986	397
85°	1921	186	2105	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 9159 cd/sqm

TEST NUMBER: P1009820

CATALOG NUMBER: S122RDIP-B290D1080UB40-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.0	1.2
10°-20°	167.5	3.4
20°-30°	215.5	4.4
30°-40°	204.5	4.2
40°-50°	175.2	3.6
50°-60°	133.4	2.7
60°-70°	84.2	1.7
70°-80°	42.0	0.9
80°-90°	14.7	0.3
90°-100°	84.6	1.7
100°-110°	269.0	5.5
110°-120°	460.3	9.4
120°-130°	605.3	12.3
130°-140°	679.5	13.8
140°-150°	666.3	13.5
150°-160°	558.9	11.4
160°-170°	370.7	7.5
170°-180°	129.6	2.6
0°-30°	443.0	9.0
0°-40°	647.4	13.2
0°-60°	956.1	19.4
0°-90°	1096.9	22.3
90°-120°	813.9	16.5
90°-150°	2764.9	56.2
90°-180°	3824.0	77.7
0°-180°	4921.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	632	632	632	632	632	
5°	633	704	635	562	633	60
15°	596	794	606	372	596	168
25°	529	424	541	270	529	243
35°	434	209	448	199	434	272
45°	326	145	340	142	326	252
55°	220	101	232	99	220	198
65°	133	52	141	59	133	132
75°	62	28	68	32	62	68
85°	14	8	15	8	14	15
90°	1	39	1	39	1	5
95°	60	72	60	72	60	67
105°	248	256	248	256	248	262
115°	462	462	462	462	462	457
125°	672	674	672	674	672	600
135°	869	880	869	880	869	672
145°	1055	1066	1055	1066	1055	659
155°	1206	1215	1206	1215	1206	555
165°	1312	1314	1312	1314	1312	370
175°	1366	1361	1366	1361	1366	130
180°	1368	1368	1368	1368	1368	

TEST NUMBER: P1009820

CATALOG NUMBER: S122RDIP-B290D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	636.4	639.1	640.4	642.1	646.1	648.7	652.7	653.6	653.1	654.9	650.1
5°	632.9	638.6	643.9	648.3	655.3	659.7	664.6	670.3	671.6	678.2	674.2
7.5°	628.1	636.4	643.9	652.7	663.2	669.0	676.4	685.2	689.2	697.1	699.3
10°	620.2	632.0	644.8	654.0	668.5	678.6	685.7	699.7	709.0	720.8	719.1
12.5°	607.4	622.8	639.9	655.3	674.2	680.8	694.0	708.5	720.4	731.4	741.0
15°	596.4	614.0	632.9	651.8	673.4	685.7	698.8	717.7	730.5	749.8	758.2
17.5°	581.5	603.9	626.3	647.4	672.9	687.0	703.2	721.7	740.6	759.1	765.7
20°	566.1	590.3	614.5	643.0	672.0	685.7	702.4	725.2	743.7	758.2	758.2
22.5°	547.6	577.1	604.8	632.0	663.7	683.5	700.6	727.4	740.6	743.7	731.8
25°	529.2	558.6	589.0	622.8	658.8	676.4	695.8	720.8	725.2	712.9	682.1
27.5°	507.2	540.2	574.5	610.9	648.7	670.7	688.3	705.0	696.6	663.7	615.8
30°	484.8	520.4	559.1	593.8	639.5	659.7	674.7	679.5	653.1	599.5	537.5
32.5°	461.5	496.2	537.1	578.9	625.0	644.3	654.0	641.3	592.9	525.2	449.6
35°	434.3	473.4	516.0	559.5	605.2	619.7	625.4	594.2	532.3	444.8	369.6
37.5°	409.6	448.8	494.5	538.9	583.3	591.2	585.4	536.7	458.0	371.4	298.0
40°	380.6	422.4	467.2	516.9	553.4	555.6	541.5	478.2	380.6	299.3	254.0
42.5°	353.8	396.0	440.8	491.4	519.1	511.6	492.7	409.6	317.8	258.0	221.5
45°	326.1	366.1	414.5	459.3	479.1	461.5	432.9	344.6	266.8	222.0	193.8
47.5°	299.3	336.7	384.6	427.7	431.2	411.4	377.6	288.8	231.2	195.1	172.3
50°	272.9	310.3	355.1	390.7	387.2	360.0	321.7	251.0	200.9	172.3	153.4
52.5°	246.6	280.4	323.9	352.1	337.1	310.7	272.9	212.7	175.4	150.3	135.8
55°	220.2	251.8	289.2	312.5	288.8	258.4	231.6	182.4	152.1	131.9	120.9
57.5°	198.2	223.3	257.6	271.6	243.1	219.3	196.0	156.9	131.9	117.4	104.6
60°	174.1	196.9	225.0	233.4	203.9	184.6	164.8	132.7	113.0	100.2	91.9
62.5°	153.4	172.3	193.8	193.8	167.9	153.4	138.5	111.2	94.9	84.8	80.9
65°	133.2	146.8	162.2	160.4	138.5	125.7	113.8	91.9	79.6	72.5	68.6
67.5°	113.4	123.9	134.1	127.9	112.1	101.1	90.1	74.3	65.9	61.1	55.8
70°	95.4	103.7	109.0	103.3	87.5	78.2	70.3	59.8	53.2	47.0	44.0
72.5°	80.0	83.5	85.3	78.2	65.0	59.8	54.1	46.6	40.9	37.8	36.9
75°	62.4	65.5	64.2	58.9	47.9	44.0	39.6	34.3	33.0	31.2	30.3
77.5°	48.8	48.8	46.6	41.8	34.3	31.2	29.4	26.8	25.5	25.1	24.2
80°	34.7	34.3	33.0	27.7	23.3	21.5	21.5	19.8	19.3	18.5	18.5
82.5°	22.9	22.9	21.1	16.7	15.4	14.9	14.5	13.6	13.6	13.2	13.2
85°	13.6	12.7	10.5	9.2	8.8	8.8	8.4	7.9	8.4	7.9	7.9
87.5°	6.2	4.8	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
90°	1.2	4.3	7.3	10.4	13.5	15.0	17.8	23.5	29.1	34.8	40.4
92.5°	25.4	27.4	29.5	31.5	33.6	34.6	34.7	35.0	35.3	35.5	35.8
95°	60.0	62.6	65.2	67.7	70.3	71.6	71.9	72.4	72.9	73.4	73.9
97.5°	100.4	102.7	105.0	107.3	109.6	110.8	111.3	112.3	113.4	114.4	115.4
100°	146.6	148.6	150.7	152.7	154.8	155.8	156.2	157.0	157.7	158.5	159.3
102.5°	195.1	196.6	198.2	199.7	201.2	202.0	202.5	203.5	204.6	205.6	206.6
105°	248.2	249.0	249.7	250.5	251.2	251.6	251.9	252.4	252.9	253.4	253.9
107.5°	301.3	302.3	303.3	304.4	305.4	305.9	305.9	305.9	305.9	305.9	305.9
110°	352.0	353.6	355.1	356.7	358.2	359.0	359.0	359.0	359.0	359.0	359.0

TEST NUMBER: P1009820

CATALOG NUMBER: S122RDIP-B290D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	407.5	409.0	410.6	412.1	413.6	414.4	414.3	414.0	413.7	413.5	413.2
115°	461.7	463.2	464.8	466.3	467.8	468.6	468.3	467.8	467.3	466.8	466.3
117.5°	516.0	518.0	520.1	522.1	524.2	525.2	524.6	523.3	522.0	520.7	519.4
120°	570.2	572.2	574.3	576.3	578.4	579.4	578.4	576.3	574.3	572.2	570.2
122.5°	619.8	622.4	625.0	627.5	630.1	631.4	630.8	629.5	628.2	626.9	625.6
125°	671.8	674.1	676.4	678.7	681.0	682.2	681.8	681.0	680.3	679.5	678.7
127.5°	722.6	725.4	728.2	731.1	733.9	735.3	734.8	733.7	732.7	731.6	730.6
130°	769.9	773.2	776.6	779.9	783.2	784.9	784.6	784.1	783.6	783.1	782.6
132.5°	823.0	825.6	828.1	830.7	833.2	834.5	834.6	834.9	835.2	835.4	835.7
135°	869.2	872.0	874.8	877.7	880.5	881.9	882.2	882.7	883.2	883.7	884.2
137.5°	919.9	922.2	924.5	926.8	929.1	930.3	930.6	931.1	931.6	932.1	932.6
140°	965.0	967.3	969.6	971.9	974.2	975.4	976.0	977.3	978.6	979.8	981.1
142.5°	1011.1	1013.4	1015.7	1018.0	1020.3	1021.5	1021.9	1022.7	1023.4	1024.2	1025.0
145°	1055.0	1056.8	1058.6	1060.4	1062.2	1063.1	1063.9	1065.4	1066.9	1068.5	1070.0
147.5°	1094.2	1096.5	1098.8	1101.1	1103.4	1104.6	1105.1	1106.1	1107.2	1108.2	1109.2
150°	1134.6	1136.2	1137.7	1139.3	1140.8	1141.6	1142.1	1143.1	1144.2	1145.2	1146.2
152.5°	1170.4	1171.9	1173.5	1175.0	1176.5	1177.3	1177.9	1179.2	1180.5	1181.8	1183.1
155°	1206.2	1207.0	1207.8	1208.5	1209.3	1209.7	1210.1	1210.8	1211.6	1212.3	1213.1
157.5°	1237.4	1237.9	1238.4	1238.9	1239.4	1239.7	1240.0	1240.5	1241.0	1241.5	1242.0
160°	1265.1	1265.6	1266.1	1266.6	1267.1	1267.4	1267.5	1267.8	1268.0	1268.3	1268.5
162.5°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.6	1290.9	1291.1	1291.4	1291.6
165°	1312.4	1312.1	1311.9	1311.6	1311.3	1311.2	1311.2	1311.2	1311.2	1311.2	1311.2
167.5°	1332.0	1331.2	1330.5	1329.7	1329.0	1328.6	1328.6	1328.6	1328.6	1328.6	1328.6
170°	1347.0	1346.2	1345.5	1344.7	1344.0	1343.6	1343.5	1343.2	1342.9	1342.7	1342.4
172.5°	1357.4	1356.6	1355.8	1355.1	1354.3	1353.9	1353.8	1353.5	1353.3	1353.0	1352.8
175°	1365.5	1364.7	1363.9	1363.2	1362.4	1362.0	1361.7	1361.2	1360.7	1360.2	1359.7
177.5°	1370.1	1369.3	1368.5	1367.8	1367.0	1366.6	1366.3	1365.8	1365.3	1364.8	1364.3
180°	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8

TEST NUMBER: P1009820

CATALOG NUMBER: S122RDIP-B290D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	654.9	655.8	657.1	663.2	664.1	665.9	665.0	665.0	665.4	664.6	665.0
5°	683.0	684.3	690.9	698.4	700.2	698.4	700.6	703.7	703.7	703.7	702.8
7.5°	709.4	714.2	721.7	732.7	734.9	737.1	741.0	738.4	739.3	743.2	741.9
10°	734.9	741.9	750.3	759.5	764.3	767.4	769.2	773.1	782.4	771.8	775.8
12.5°	759.1	769.2	778.0	788.1	791.6	795.5	796.9	800.4	800.4	799.9	803.0
15°	774.9	784.1	792.0	798.6	799.5	798.6	797.7	798.2	799.5	794.2	797.3
17.5°	778.4	779.3	781.9	779.3	779.7	770.5	765.2	763.9	751.6	752.0	762.1
20°	761.3	746.3	742.4	727.9	719.1	695.3	694.5	687.9	661.9	669.8	668.1
22.5°	714.2	688.7	654.9	638.2	629.8	604.8	585.4	571.8	562.6	553.4	549.4
25°	652.3	610.9	563.0	530.1	525.2	501.9	466.3	449.6	429.9	423.7	434.3
27.5°	572.3	518.6	464.6	414.0	404.8	383.7	365.7	353.8	331.0	329.6	330.5
30°	463.7	409.6	364.4	331.4	308.5	298.9	287.0	278.2	269.0	272.5	273.4
32.5°	381.1	329.6	287.4	269.9	259.3	253.2	243.1	237.3	233.4	232.1	231.6
35°	302.8	268.6	249.7	232.5	226.4	222.0	214.5	211.9	208.3	208.8	208.8
37.5°	259.3	230.8	216.7	207.9	202.2	200.0	195.1	192.5	190.3	189.4	190.8
40°	223.7	203.9	195.1	187.2	182.4	181.5	178.9	175.8	173.2	173.6	174.9
42.5°	197.8	186.4	175.8	169.7	166.1	164.8	162.6	160.4	160.4	159.1	158.7
45°	177.1	167.9	159.1	153.4	151.2	149.4	146.8	146.4	144.6	145.0	145.5
47.5°	158.7	151.2	144.6	138.9	136.7	136.3	133.6	131.9	131.9	131.4	131.0
50°	142.0	134.5	128.8	125.7	122.6	121.7	121.3	120.9	120.0	120.0	120.4
52.5°	128.3	120.9	116.5	113.8	112.1	111.2	111.2	110.8	110.8	110.8	110.3
55°	113.4	107.2	103.7	102.8	102.0	101.5	101.1	100.2	99.8	100.7	99.8
57.5°	99.3	97.1	94.1	93.2	91.0	91.0	89.7	88.8	87.9	88.8	88.8
60°	88.3	85.3	83.5	80.9	79.1	77.4	75.2	74.7	73.8	73.4	73.0
62.5°	76.9	74.3	69.9	65.9	63.3	61.5	60.7	60.2	60.2	59.8	59.8
65°	64.2	58.0	55.8	54.5	54.1	53.6	52.7	52.3	52.7	52.3	52.7
67.5°	50.1	49.2	47.9	47.0	46.6	46.2	46.2	45.7	45.7	45.7	45.7
70°	43.5	41.3	40.9	40.0	40.0	39.6	39.6	39.6	39.6	39.1	40.0
72.5°	36.0	34.7	34.3	33.8	33.8	33.8	33.4	33.4	33.4	33.0	33.4
75°	29.4	29.0	28.1	28.1	27.7	28.1	27.7	27.7	27.3	27.7	27.7
77.5°	23.7	23.3	22.9	22.9	22.4	22.4	22.4	22.4	22.4	22.4	22.9
80°	18.0	17.6	17.1	17.6	17.1	17.6	17.1	17.1	17.6	17.1	17.1
82.5°	13.2	12.7	12.7	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3
85°	7.9	7.5	7.5	7.9	7.5	7.9	7.5	7.5	7.5	7.9	7.9
87.5°	3.5	4.0	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	4.0
90°	39.9	39.4	38.9	38.4	38.1	38.2	38.5	38.7	39.0	39.2	39.0
92.5°	36.0	36.3	36.5	36.8	36.9	36.9	36.9	36.9	36.9	36.9	36.9
95°	73.9	73.9	73.9	73.9	73.9	73.6	73.1	72.6	72.1	71.6	72.1
97.5°	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4
100°	159.3	159.3	159.3	159.3	159.3	159.2	158.9	158.6	158.4	158.1	158.4
102.5°	206.9	207.1	207.4	207.7	207.8	207.7	207.4	207.1	206.9	206.6	206.9
105°	254.4	254.9	255.4	255.9	256.2	256.2	256.2	256.2	256.2	256.2	256.2
107.5°	306.1	306.4	306.6	306.9	307.0	306.4	305.1	303.8	302.6	301.3	302.6
110°	359.0	359.0	359.0	359.0	359.0	358.6	357.8	357.1	356.3	355.5	356.3

TEST NUMBER: P1009820

CATALOG NUMBER: S122RDIP-B290D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	412.4	411.7	410.9	410.2	409.8	409.5	409.0	408.5	408.0	407.5	408.0
115°	466.1	465.8	465.6	465.3	465.2	464.8	464.0	463.3	462.5	461.7	462.5
117.5°	518.6	517.9	517.1	516.4	516.0	515.6	514.8	514.1	513.3	512.5	513.3
120°	570.2	570.2	570.2	570.2	570.2	569.8	569.0	568.3	567.5	566.7	567.5
122.5°	624.8	624.0	623.3	622.5	622.1	621.8	621.3	620.8	620.3	619.8	620.3
125°	677.9	677.1	676.4	675.6	675.2	675.1	674.8	674.6	674.3	674.1	674.3
127.5°	729.6	728.6	727.5	726.5	726.0	725.6	724.9	724.1	723.4	722.6	723.4
130°	782.1	781.6	781.1	780.6	780.3	779.8	778.8	777.7	776.7	775.7	776.7
132.5°	834.4	833.1	831.8	830.5	829.9	829.5	828.8	828.0	827.3	826.5	827.3
135°	883.9	883.7	883.4	883.1	883.0	882.6	881.8	881.1	880.3	879.5	880.3
137.5°	932.4	932.1	931.9	931.6	931.5	931.0	930.0	928.9	927.9	926.9	927.9
140°	981.1	981.1	981.1	981.1	981.1	980.6	979.6	978.5	977.5	976.5	977.5
142.5°	1025.2	1025.5	1025.7	1026.0	1026.1	1025.6	1024.6	1023.5	1022.5	1021.5	1022.5
145°	1070.3	1070.5	1070.8	1071.1	1071.2	1070.7	1069.6	1068.6	1067.5	1066.5	1067.5
147.5°	1109.7	1110.3	1110.8	1111.3	1111.6	1111.1	1110.0	1109.0	1107.9	1106.9	1107.9
150°	1147.0	1147.7	1148.5	1149.2	1149.6	1149.2	1148.5	1147.7	1147.0	1146.2	1147.0
152.5°	1184.1	1185.1	1186.2	1187.2	1187.7	1187.2	1186.2	1185.1	1184.1	1183.1	1184.1
155°	1214.4	1215.7	1217.0	1218.3	1218.9	1218.5	1217.7	1217.0	1216.2	1215.4	1216.2
157.5°	1243.8	1245.6	1247.4	1249.2	1250.1	1249.5	1248.2	1246.9	1245.6	1244.3	1245.6
160°	1270.1	1271.6	1273.2	1274.7	1275.5	1275.0	1273.9	1272.9	1271.8	1270.8	1271.8
162.5°	1293.4	1295.2	1297.0	1298.8	1299.7	1299.1	1297.8	1296.5	1295.2	1293.9	1295.2
165°	1313.0	1314.8	1316.6	1318.4	1319.3	1318.7	1317.4	1316.1	1314.8	1313.5	1314.8
167.5°	1330.4	1332.2	1333.9	1335.7	1336.6	1336.0	1334.7	1333.4	1332.2	1330.9	1332.2
170°	1344.2	1346.0	1347.8	1349.6	1350.5	1349.7	1348.2	1346.7	1345.1	1343.6	1345.1
172.5°	1354.6	1356.4	1358.2	1360.0	1360.9	1360.1	1358.6	1357.0	1355.5	1353.9	1355.5
175°	1361.5	1363.3	1365.1	1366.9	1367.8	1367.0	1365.5	1364.0	1362.4	1360.9	1362.4
177.5°	1365.9	1367.4	1369.0	1370.5	1371.3	1370.5	1369.0	1367.4	1365.9	1364.3	1365.9
180°	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8

TEST NUMBER: P1009820

CATALOG NUMBER: S122RDIP-B290D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	666.8	663.7	662.8	663.7	662.8	663.2	660.2	648.7	651.8	647.0	649.6
5°	704.6	701.9	696.2	695.3	694.5	693.6	689.2	679.1	675.1	668.5	668.1
7.5°	740.6	740.6	736.2	733.1	729.2	726.1	720.4	705.4	699.3	691.4	687.0
10°	776.2	764.8	769.6	766.5	756.9	755.1	744.6	735.8	723.9	716.0	709.0
12.5°	801.7	798.2	793.8	791.1	788.5	782.8	775.8	753.3	747.2	731.4	723.5
15°	800.8	798.6	799.9	799.9	799.1	797.7	792.0	775.8	765.2	749.8	736.2
17.5°	757.7	763.5	769.2	773.1	781.9	785.9	791.1	781.5	774.9	761.7	747.2
20°	682.6	696.6	713.4	716.9	724.8	748.1	758.6	767.0	769.6	765.2	753.3
22.5°	578.0	589.8	630.3	629.4	640.8	668.5	699.3	724.3	744.1	755.1	750.7
25°	452.7	469.4	491.0	507.2	544.6	585.9	624.1	664.1	698.4	728.7	736.2
27.5°	342.4	364.4	381.5	403.0	421.9	470.7	520.0	582.4	622.4	679.9	709.8
30°	276.9	287.0	304.2	314.3	323.5	360.9	416.7	478.2	548.5	614.9	666.3
32.5°	236.5	243.5	256.2	260.6	270.3	295.4	330.5	386.8	459.3	539.7	607.4
35°	212.3	219.8	222.4	226.4	234.3	250.1	274.3	315.1	380.6	459.3	540.2
37.5°	191.6	195.6	203.1	205.7	208.3	220.2	236.5	265.0	308.5	373.2	462.8
40°	177.1	179.3	183.3	185.5	187.2	195.6	210.1	229.4	261.5	310.7	393.4
42.5°	161.7	164.4	167.0	169.7	171.9	178.4	187.2	205.7	227.2	264.6	324.4
45°	146.8	148.6	151.6	153.4	156.5	161.7	169.7	182.4	201.7	225.5	273.8
47.5°	133.2	135.4	136.7	138.9	141.1	146.8	154.3	162.6	178.4	201.7	236.9
50°	120.9	123.5	125.3	125.7	127.5	132.7	138.9	148.1	158.2	176.2	207.0
52.5°	112.1	112.5	113.8	115.6	115.2	118.2	123.9	131.0	141.5	156.0	178.4
55°	102.0	103.3	104.2	104.6	104.6	107.2	110.3	116.9	125.3	137.1	156.0
57.5°	89.2	90.5	93.2	94.1	95.4	96.7	98.0	102.4	109.4	120.9	136.3
60°	76.0	76.9	79.6	81.3	82.2	85.7	87.5	91.0	94.9	103.3	117.8
62.5°	61.1	62.0	63.3	65.0	66.8	72.1	76.5	80.0	83.1	88.8	100.7
65°	53.2	53.6	54.5	54.9	55.4	57.6	61.5	66.4	72.1	76.5	83.5
67.5°	46.2	46.6	47.0	47.9	48.3	48.8	50.5	51.9	57.6	63.7	69.0
70°	39.6	40.4	40.9	40.9	41.3	42.2	43.1	44.8	46.6	49.7	56.3
72.5°	33.4	33.8	34.7	34.7	34.7	35.6	36.5	37.4	38.2	40.0	42.6
75°	27.7	28.6	28.6	28.6	29.0	29.0	29.9	30.8	31.6	33.0	33.8
77.5°	22.9	22.9	22.9	22.9	23.3	23.3	23.7	24.6	25.1	25.5	26.4
80°	17.1	17.6	17.6	17.6	18.0	18.0	18.0	18.9	19.3	19.3	20.2
82.5°	12.7	12.7	12.7	13.2	12.7	13.2	13.2	13.6	13.2	13.6	14.1
85°	7.9	7.9	7.9	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.8
87.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.4	4.0	4.0
90°	38.7	38.5	38.2	38.1	38.4	38.9	39.4	39.9	40.4	34.8	29.1
92.5°	36.9	36.9	36.9	36.9	36.8	36.5	36.3	36.0	35.8	35.5	35.3
95°	72.6	73.1	73.6	73.9	73.9	73.9	73.9	73.9	73.9	73.4	72.9
97.5°	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	114.4	113.4
100°	158.6	158.9	159.2	159.3	159.3	159.3	159.3	159.3	159.3	158.5	157.7
102.5°	207.1	207.4	207.7	207.8	207.7	207.4	207.1	206.9	206.6	205.6	204.6
105°	256.2	256.2	256.2	256.2	255.9	255.4	254.9	254.4	253.9	253.4	252.9
107.5°	303.8	305.1	306.4	307.0	306.9	306.6	306.4	306.1	305.9	305.9	305.9
110°	357.1	357.8	358.6	359.0	359.0	359.0	359.0	359.0	359.0	359.0	359.0

TEST NUMBER: P1009820

CATALOG NUMBER: S122RDIP-B290D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	408.5	409.0	409.5	409.8	410.2	410.9	411.7	412.4	413.2	413.5	413.7
115°	463.3	464.0	464.8	465.2	465.3	465.6	465.8	466.1	466.3	466.8	467.3
117.5°	514.1	514.8	515.6	516.0	516.4	517.1	517.9	518.6	519.4	520.7	522.0
120°	568.3	569.0	569.8	570.2	570.2	570.2	570.2	570.2	570.2	572.2	574.3
122.5°	620.8	621.3	621.8	622.1	622.5	623.3	624.0	624.8	625.6	626.9	628.2
125°	674.6	674.8	675.1	675.2	675.6	676.4	677.1	677.9	678.7	679.5	680.3
127.5°	724.1	724.9	725.6	726.0	726.5	727.5	728.6	729.6	730.6	731.6	732.7
130°	777.7	778.8	779.8	780.3	780.6	781.1	781.6	782.1	782.6	783.1	783.6
132.5°	828.0	828.8	829.5	829.9	830.5	831.8	833.1	834.4	835.7	835.4	835.2
135°	881.1	881.8	882.6	883.0	883.1	883.4	883.7	883.9	884.2	883.7	883.2
137.5°	928.9	930.0	931.0	931.5	931.6	931.9	932.1	932.4	932.6	932.1	931.6
140°	978.5	979.6	980.6	981.1	981.1	981.1	981.1	981.1	981.1	979.8	978.6
142.5°	1023.5	1024.6	1025.6	1026.1	1026.0	1025.7	1025.5	1025.2	1025.0	1024.2	1023.4
145°	1068.6	1069.6	1070.7	1071.2	1071.1	1070.8	1070.5	1070.3	1070.0	1068.5	1066.9
147.5°	1109.0	1110.0	1111.1	1111.6	1111.3	1110.8	1110.3	1109.7	1109.2	1108.2	1107.2
150°	1147.7	1148.5	1149.2	1149.6	1149.2	1148.5	1147.7	1147.0	1146.2	1145.2	1144.2
152.5°	1185.1	1186.2	1187.2	1187.7	1187.2	1186.2	1185.1	1184.1	1183.1	1181.8	1180.5
155°	1217.0	1217.7	1218.5	1218.9	1218.3	1217.0	1215.7	1214.4	1213.1	1212.3	1211.6
157.5°	1246.9	1248.2	1249.5	1250.1	1249.2	1247.4	1245.6	1243.8	1242.0	1241.5	1241.0
160°	1272.9	1273.9	1275.0	1275.5	1274.7	1273.2	1271.6	1270.1	1268.5	1268.3	1268.0
162.5°	1296.5	1297.8	1299.1	1299.7	1298.8	1297.0	1295.2	1293.4	1291.6	1291.4	1291.1
165°	1316.1	1317.4	1318.7	1319.3	1318.4	1316.6	1314.8	1313.0	1311.2	1311.2	1311.2
167.5°	1333.4	1334.7	1336.0	1336.6	1335.7	1333.9	1332.2	1330.4	1328.6	1328.6	1328.6
170°	1346.7	1348.2	1349.7	1350.5	1349.6	1347.8	1346.0	1344.2	1342.4	1342.7	1342.9
172.5°	1357.0	1358.6	1360.1	1360.9	1360.0	1358.2	1356.4	1354.6	1352.8	1353.0	1353.3
175°	1364.0	1365.5	1367.0	1367.8	1366.9	1365.1	1363.3	1361.5	1359.7	1360.2	1360.7
177.5°	1367.4	1369.0	1370.5	1371.3	1370.5	1369.0	1367.4	1365.9	1364.3	1364.8	1365.3
180°	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8

TEST NUMBER: P1009820

CATALOG NUMBER: S122RDIP-B290D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	645.7	643.5	643.5	642.1	642.1	635.1	635.1	637.3	634.7	631.6	627.2
5°	662.4	657.5	656.2	654.5	648.7	639.9	636.4	635.1	629.8	623.2	615.8
7.5°	678.2	670.3	666.3	662.4	654.9	642.6	635.6	630.7	622.8	612.7	603.0
10°	693.6	683.5	673.4	668.5	658.0	642.6	632.5	624.6	613.1	599.5	585.9
12.5°	707.6	686.5	684.8	675.1	659.7	642.1	626.8	615.3	600.8	585.0	569.2
15°	719.9	698.4	687.9	679.1	658.8	636.9	620.6	606.5	587.2	569.2	549.8
17.5°	726.1	702.8	695.8	681.3	660.6	632.0	610.1	592.9	571.8	550.3	528.3
20°	732.3	705.0	693.6	683.5	655.3	622.8	598.2	578.4	555.1	529.6	505.5
22.5°	735.3	705.0	691.4	677.3	650.1	612.7	583.7	560.4	533.1	507.2	478.2
25°	730.1	702.4	686.1	671.6	640.8	600.4	567.0	540.6	511.6	482.2	452.7
27.5°	716.9	696.2	677.3	662.4	628.1	584.6	549.4	519.5	489.6	456.7	426.8
30°	692.3	683.0	668.1	651.4	614.0	570.5	528.7	498.0	465.0	432.1	400.8
32.5°	654.0	661.9	652.3	637.8	597.3	551.2	506.8	475.6	439.5	403.9	375.4
35°	607.4	635.6	630.3	620.2	579.7	530.5	486.1	448.3	412.3	376.2	347.7
37.5°	556.4	599.1	603.5	597.3	559.5	509.4	460.6	423.7	386.8	350.3	321.3
40°	486.6	552.0	566.1	568.7	538.4	483.9	432.9	396.9	360.4	324.8	289.6
42.5°	422.4	505.0	522.6	533.6	511.6	458.9	407.4	367.4	331.4	299.3	264.2
45°	362.2	448.3	476.9	491.0	481.3	430.3	377.1	339.8	306.8	277.3	243.5
47.5°	300.2	386.8	426.8	449.2	449.2	401.3	348.1	311.2	279.5	254.5	224.6
50°	258.9	331.0	372.3	401.7	409.6	371.8	321.7	285.7	255.8	228.6	205.7
52.5°	220.6	285.3	319.5	350.3	373.2	340.2	292.3	259.8	230.3	204.8	186.8
55°	190.8	239.1	270.3	304.2	329.6	308.1	263.7	232.1	206.6	185.5	170.1
57.5°	162.2	204.4	229.9	259.8	287.0	270.7	235.1	207.9	185.5	167.0	153.4
60°	138.0	172.3	192.1	215.4	249.2	237.8	208.3	183.3	165.3	148.6	137.1
62.5°	117.4	144.6	161.3	178.0	208.8	203.5	180.6	161.3	145.9	131.9	122.2
65°	96.3	118.7	131.9	146.4	171.0	173.2	154.7	141.1	127.0	114.7	105.9
67.5°	77.8	95.4	107.2	119.6	139.3	145.5	132.7	121.3	109.4	99.3	91.4
70°	62.9	75.2	83.9	93.6	109.9	117.4	110.8	102.8	93.2	84.8	77.8
72.5°	49.7	57.6	62.9	70.3	83.5	91.0	90.5	83.5	76.5	70.8	65.0
75°	36.5	42.6	47.0	51.9	62.4	69.4	71.2	68.1	61.1	56.7	52.3
77.5°	27.7	31.2	33.4	36.9	44.4	50.5	53.2	52.3	47.5	44.0	40.9
80°	21.1	22.0	22.9	24.2	30.3	36.0	37.8	37.4	34.7	33.4	29.9
82.5°	14.9	15.4	15.8	16.3	18.5	23.3	25.1	25.9	23.7	22.4	19.3
85°	8.8	9.2	9.2	10.1	10.5	11.9	14.9	14.9	14.5	12.7	12.3
87.5°	4.4	4.4	4.0	4.0	4.4	4.8	5.7	6.6	5.7	5.3	4.8
90°	23.5	17.8	15.0	13.5	10.4	7.3	4.3	1.2	4.3	7.3	10.4
92.5°	35.0	34.7	34.6	33.6	31.5	29.5	27.4	25.4	27.4	29.5	31.5
95°	72.4	71.9	71.6	70.3	67.7	65.2	62.6	60.0	62.6	65.2	67.7
97.5°	112.3	111.3	110.8	109.6	107.3	105.0	102.7	100.4	102.7	105.0	107.3
100°	157.0	156.2	155.8	154.8	152.7	150.7	148.6	146.6	148.6	150.7	152.7
102.5°	203.5	202.5	202.0	201.2	199.7	198.2	196.6	195.1	196.6	198.2	199.7
105°	252.4	251.9	251.6	251.2	250.5	249.7	249.0	248.2	249.0	249.7	250.5
107.5°	305.9	305.9	305.9	305.4	304.4	303.3	302.3	301.3	302.3	303.3	304.4
110°	359.0	359.0	359.0	358.2	356.7	355.1	353.6	352.0	353.6	355.1	356.7

TEST NUMBER: P1009820

CATALOG NUMBER: S122RDIP-B290D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	414.0	414.3	414.4	413.6	412.1	410.6	409.0	407.5	409.0	410.6	412.1
115°	467.8	468.3	468.6	467.8	466.3	464.8	463.2	461.7	463.2	464.8	466.3
117.5°	523.3	524.6	525.2	524.2	522.1	520.1	518.0	516.0	518.0	520.1	522.1
120°	576.3	578.4	579.4	578.4	576.3	574.3	572.2	570.2	572.2	574.3	576.3
122.5°	629.5	630.8	631.4	630.1	627.5	625.0	622.4	619.8	622.4	625.0	627.5
125°	681.0	681.8	682.2	681.0	678.7	676.4	674.1	671.8	674.1	676.4	678.7
127.5°	733.7	734.8	735.3	733.9	731.1	728.2	725.4	722.6	725.4	728.2	731.1
130°	784.1	784.6	784.9	783.2	779.9	776.6	773.2	769.9	773.2	776.6	779.9
132.5°	834.9	834.6	834.5	833.2	830.7	828.1	825.6	823.0	825.6	828.1	830.7
135°	882.7	882.2	881.9	880.5	877.7	874.8	872.0	869.2	872.0	874.8	877.7
137.5°	931.1	930.6	930.3	929.1	926.8	924.5	922.2	919.9	922.2	924.5	926.8
140°	977.3	976.0	975.4	974.2	971.9	969.6	967.3	965.0	967.3	969.6	971.9
142.5°	1022.7	1021.9	1021.5	1020.3	1018.0	1015.7	1013.4	1011.1	1013.4	1015.7	1018.0
145°	1065.4	1063.9	1063.1	1062.2	1060.4	1058.6	1056.8	1055.0	1056.8	1058.6	1060.4
147.5°	1106.1	1105.1	1104.6	1103.4	1101.1	1098.8	1096.5	1094.2	1096.5	1098.8	1101.1
150°	1143.1	1142.1	1141.6	1140.8	1139.3	1137.7	1136.2	1134.6	1136.2	1137.7	1139.3
152.5°	1179.2	1177.9	1177.3	1176.5	1175.0	1173.5	1171.9	1170.4	1171.9	1173.5	1175.0
155°	1210.8	1210.1	1209.7	1209.3	1208.5	1207.8	1207.0	1206.2	1207.0	1207.8	1208.5
157.5°	1240.5	1240.0	1239.7	1239.4	1238.9	1238.4	1237.9	1237.4	1237.9	1238.4	1238.9
160°	1267.8	1267.5	1267.4	1267.1	1266.6	1266.1	1265.6	1265.1	1265.6	1266.1	1266.6
162.5°	1290.9	1290.6	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
165°	1311.2	1311.2	1311.2	1311.3	1311.6	1311.9	1312.1	1312.4	1312.1	1311.9	1311.6
167.5°	1328.6	1328.6	1328.6	1329.0	1329.7	1330.5	1331.2	1332.0	1331.2	1330.5	1329.7
170°	1343.2	1343.5	1343.6	1344.0	1344.7	1345.5	1346.2	1347.0	1346.2	1345.5	1344.7
172.5°	1353.5	1353.8	1353.9	1354.3	1355.1	1355.8	1356.6	1357.4	1356.6	1355.8	1355.1
175°	1361.2	1361.7	1362.0	1362.4	1363.2	1363.9	1364.7	1365.5	1364.7	1363.9	1363.2
177.5°	1365.8	1366.3	1366.6	1367.0	1367.8	1368.5	1369.3	1370.1	1369.3	1368.5	1367.8
180°	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8

TEST NUMBER: P1009820

CATALOG NUMBER: S122RDIP-B290D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	625.4	625.9	627.2	623.2	617.1	614.5	606.5	605.2	603.9	603.9	605.2
5°	611.4	609.6	610.1	602.6	593.8	588.5	577.5	579.3	573.6	570.1	570.9
7.5°	596.0	591.2	590.7	581.1	570.1	560.4	549.0	546.3	541.1	534.9	532.3
10°	576.7	573.1	566.5	555.6	541.5	533.6	518.2	509.0	507.7	498.4	494.9
12.5°	556.9	550.7	544.1	528.7	512.9	500.2	488.8	478.6	471.6	463.7	458.4
15°	534.0	526.6	519.1	502.8	484.4	471.6	454.5	439.5	418.9	402.6	393.4
17.5°	509.0	500.6	490.5	472.5	454.5	436.9	405.2	387.7	373.2	363.5	357.8
20°	483.0	473.8	463.7	445.7	414.5	383.7	366.1	352.5	343.7	334.0	327.0
22.5°	455.8	446.1	435.1	407.0	374.0	352.5	338.9	326.1	313.4	308.1	304.6
25°	430.3	421.5	407.4	369.2	343.3	323.5	308.1	299.8	293.2	286.1	279.5
27.5°	403.9	387.7	367.9	335.8	319.5	299.3	288.3	282.2	270.7	265.9	262.8
30°	372.3	354.3	335.4	312.5	293.6	279.5	269.4	259.3	252.7	247.9	242.6
32.5°	340.2	323.1	311.2	287.4	273.4	258.9	249.2	243.1	233.4	230.3	228.1
35°	312.5	298.0	287.4	268.1	254.9	241.7	234.7	225.5	219.3	213.6	210.1
37.5°	285.3	277.3	266.4	250.1	236.0	225.5	215.8	212.7	204.4	201.3	197.8
40°	266.4	254.5	245.3	231.2	219.3	207.9	201.7	194.7	189.0	184.2	182.8
42.5°	243.5	234.7	229.4	214.0	201.7	195.1	187.7	179.8	175.4	171.4	166.6
45°	226.4	218.4	211.0	198.7	187.7	179.3	172.7	167.5	160.0	158.2	150.8
47.5°	208.3	200.4	194.7	182.4	172.3	164.4	159.5	152.5	146.4	142.4	138.9
50°	190.3	183.7	178.4	167.9	159.1	150.8	144.2	137.1	134.5	127.9	125.7
52.5°	173.2	168.8	163.1	153.0	144.2	137.1	130.1	124.4	120.4	116.9	114.3
55°	158.7	151.6	149.0	138.0	130.5	123.1	116.9	113.4	108.6	106.4	104.2
57.5°	142.4	138.5	134.1	125.7	117.4	110.3	105.9	100.7	98.0	95.4	93.6
60°	128.3	122.6	119.1	112.1	104.6	98.0	94.1	90.1	86.6	84.4	80.9
62.5°	112.1	107.7	105.5	98.0	91.9	85.7	82.2	78.2	75.6	71.6	67.2
65°	98.0	94.5	91.9	85.7	80.0	74.3	70.8	65.9	62.4	60.2	59.8
67.5°	85.7	83.1	79.1	73.4	67.7	63.3	59.3	55.4	54.9	54.1	54.1
70°	72.1	69.4	67.2	61.1	56.3	51.4	50.5	49.2	47.9	47.5	46.6
72.5°	60.2	58.0	55.4	50.1	45.3	44.0	43.1	42.2	40.9	40.4	40.0
75°	48.8	45.7	44.0	39.1	37.8	36.9	36.0	34.7	33.8	33.4	32.5
77.5°	37.4	34.3	34.3	31.6	30.8	29.4	28.6	27.7	27.3	26.4	26.4
80°	26.4	26.4	25.5	24.2	22.9	22.4	21.1	20.7	20.2	20.7	19.8
82.5°	19.3	17.6	17.6	16.7	15.8	15.4	14.5	14.5	14.1	14.1	14.1
85°	11.0	11.0	10.5	9.7	9.2	9.2	8.8	8.8	8.4	8.4	7.9
87.5°	4.4	4.0	4.4	4.0	4.0	3.5	3.5	3.5	3.1	3.5	3.1
90°	13.5	15.0	17.8	23.5	29.1	34.8	40.4	39.9	39.4	38.9	38.4
92.5°	33.6	34.6	34.7	35.0	35.3	35.5	35.8	36.0	36.3	36.5	36.8
95°	70.3	71.6	71.9	72.4	72.9	73.4	73.9	73.9	73.9	73.9	73.9
97.5°	109.6	110.8	111.3	112.3	113.4	114.4	115.4	115.4	115.4	115.4	115.4
100°	154.8	155.8	156.2	157.0	157.7	158.5	159.3	159.3	159.3	159.3	159.3
102.5°	201.2	202.0	202.5	203.5	204.6	205.6	206.6	206.9	207.1	207.4	207.7
105°	251.2	251.6	251.9	252.4	252.9	253.4	253.9	254.4	254.9	255.4	255.9
107.5°	305.4	305.9	305.9	305.9	305.9	305.9	305.9	306.1	306.4	306.6	306.9
110°	358.2	359.0	359.0	359.0	359.0	359.0	359.0	359.0	359.0	359.0	359.0

TEST NUMBER: P1009820

CATALOG NUMBER: S122RDIP-B290D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	413.6	414.4	414.3	414.0	413.7	413.5	413.2	412.4	411.7	410.9	410.2
115°	467.8	468.6	468.3	467.8	467.3	466.8	466.3	466.1	465.8	465.6	465.3
117.5°	524.2	525.2	524.6	523.3	522.0	520.7	519.4	518.6	517.9	517.1	516.4
120°	578.4	579.4	578.4	576.3	574.3	572.2	570.2	570.2	570.2	570.2	570.2
122.5°	630.1	631.4	630.8	629.5	628.2	626.9	625.6	624.8	624.0	623.3	622.5
125°	681.0	682.2	681.8	681.0	680.3	679.5	678.7	677.9	677.1	676.4	675.6
127.5°	733.9	735.3	734.8	733.7	732.7	731.6	730.6	729.6	728.6	727.5	726.5
130°	783.2	784.9	784.6	784.1	783.6	783.1	782.6	782.1	781.6	781.1	780.6
132.5°	833.2	834.5	834.6	834.9	835.2	835.4	835.7	834.4	833.1	831.8	830.5
135°	880.5	881.9	882.2	882.7	883.2	883.7	884.2	883.9	883.7	883.4	883.1
137.5°	929.1	930.3	930.6	931.1	931.6	932.1	932.6	932.4	932.1	931.9	931.6
140°	974.2	975.4	976.0	977.3	978.6	979.8	981.1	981.1	981.1	981.1	981.1
142.5°	1020.3	1021.5	1021.9	1022.7	1023.4	1024.2	1025.0	1025.2	1025.5	1025.7	1026.0
145°	1062.2	1063.1	1063.9	1065.4	1066.9	1068.5	1070.0	1070.3	1070.5	1070.8	1071.1
147.5°	1103.4	1104.6	1105.1	1106.1	1107.2	1108.2	1109.2	1109.7	1110.3	1110.8	1111.3
150°	1140.8	1141.6	1142.1	1143.1	1144.2	1145.2	1146.2	1147.0	1147.7	1148.5	1149.2
152.5°	1176.5	1177.3	1177.9	1179.2	1180.5	1181.8	1183.1	1184.1	1185.1	1186.2	1187.2
155°	1209.3	1209.7	1210.1	1210.8	1211.6	1212.3	1213.1	1214.4	1215.7	1217.0	1218.3
157.5°	1239.4	1239.7	1240.0	1240.5	1241.0	1241.5	1242.0	1243.8	1245.6	1247.4	1249.2
160°	1267.1	1267.4	1267.5	1267.8	1268.0	1268.3	1268.5	1270.1	1271.6	1273.2	1274.7
162.5°	1290.5	1290.5	1290.6	1290.9	1291.1	1291.4	1291.6	1293.4	1295.2	1297.0	1298.8
165°	1311.3	1311.2	1311.2	1311.2	1311.2	1311.2	1311.2	1313.0	1314.8	1316.6	1318.4
167.5°	1329.0	1328.6	1328.6	1328.6	1328.6	1328.6	1328.6	1330.4	1332.2	1333.9	1335.7
170°	1344.0	1343.6	1343.5	1343.2	1342.9	1342.7	1342.4	1344.2	1346.0	1347.8	1349.6
172.5°	1354.3	1353.9	1353.8	1353.5	1353.3	1353.0	1352.8	1354.6	1356.4	1358.2	1360.0
175°	1362.4	1362.0	1361.7	1361.2	1360.7	1360.2	1359.7	1361.5	1363.3	1365.1	1366.9
177.5°	1367.0	1366.6	1366.3	1365.8	1365.3	1364.8	1364.3	1365.9	1367.4	1369.0	1370.5
180°	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8

TEST NUMBER: P1009820

CATALOG NUMBER: S122RDIP-B290D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	605.2	604.3	601.7	602.6	601.3	601.3	600.4	600.4	600.4	602.6	601.3
5°	572.3	569.2	566.1	564.8	563.5	562.2	562.2	561.7	565.7	564.8	568.3
7.5°	531.4	530.5	524.4	524.4	522.2	521.3	523.5	523.9	524.4	525.2	527.4
10°	494.9	492.7	483.9	484.8	483.5	481.7	483.0	482.2	485.2	486.1	485.2
12.5°	451.8	447.9	438.2	433.4	428.1	424.1	429.0	425.5	437.8	441.3	451.0
15°	394.7	387.2	380.6	380.6	375.8	372.3	374.5	378.4	381.1	385.0	386.8
17.5°	356.5	353.4	348.1	345.0	343.7	342.4	342.4	344.1	349.9	349.4	352.9
20°	323.9	322.2	319.5	315.6	314.3	313.4	313.4	313.4	317.3	320.9	323.1
22.5°	301.5	300.2	298.4	293.2	290.5	289.6	291.8	293.2	296.2	298.9	301.1
25°	279.1	276.0	272.9	271.2	269.9	269.9	270.7	271.2	272.5	273.8	276.5
27.5°	260.6	258.4	254.0	249.2	249.2	247.9	248.8	249.7	252.7	257.1	259.3
30°	240.0	239.5	237.8	236.0	234.3	233.4	235.1	236.5	236.9	239.1	239.1
32.5°	225.0	222.0	218.9	217.1	216.2	215.8	216.2	218.0	218.0	220.6	223.7
35°	210.1	208.3	205.3	202.2	201.3	199.1	200.9	202.6	205.7	207.0	208.3
37.5°	193.8	191.6	190.3	189.4	187.7	188.1	186.8	189.4	192.1	191.6	192.5
40°	181.5	177.6	173.6	173.2	172.7	172.3	172.3	172.7	174.5	176.2	178.9
42.5°	165.7	164.4	160.9	157.4	156.5	155.6	154.7	156.5	160.0	163.1	164.4
45°	149.4	147.7	146.8	144.2	142.4	142.0	141.1	143.3	146.4	147.7	148.6
47.5°	134.5	134.1	131.4	131.9	130.5	131.0	130.5	131.9	131.9	133.2	134.1
50°	124.4	123.1	121.7	120.9	119.6	119.6	119.1	119.6	121.3	123.1	122.6
52.5°	114.3	112.1	111.6	111.2	110.3	111.2	109.9	110.3	112.1	113.0	112.5
55°	102.4	102.0	101.1	100.2	99.8	99.3	99.3	99.3	101.1	102.4	102.8
57.5°	93.2	91.0	89.2	89.2	87.5	87.0	87.9	88.3	89.7	90.5	91.4
60°	80.4	79.6	76.9	75.6	73.0	72.5	72.5	74.3	76.5	79.6	80.4
62.5°	66.8	65.5	65.0	65.0	65.0	65.0	65.0	65.0	65.0	65.5	65.5
65°	59.3	59.8	59.3	58.9	59.3	59.3	58.9	58.9	58.9	59.3	59.8
67.5°	53.2	52.7	53.2	52.7	52.3	52.3	51.9	52.3	52.7	53.2	53.2
70°	46.2	46.2	45.7	46.2	45.7	45.3	44.8	44.8	45.7	46.2	46.2
72.5°	39.6	39.6	39.1	39.1	38.2	38.2	38.7	38.2	38.2	39.6	39.6
75°	33.0	32.5	32.1	32.1	31.6	31.6	31.6	31.2	32.1	32.1	32.5
77.5°	25.9	25.9	25.9	25.5	25.5	25.1	25.1	25.5	25.5	25.5	25.9
80°	19.8	19.8	19.8	19.3	18.9	18.9	18.9	18.9	18.9	19.3	18.9
82.5°	13.6	13.6	13.6	13.6	13.6	13.2	13.2	13.2	13.6	13.6	13.2
85°	8.4	7.9	8.4	8.4	7.9	8.4	7.9	7.9	7.5	7.5	7.9
87.5°	3.5	3.1	2.6	2.6	3.1	2.6	2.6	2.6	3.1	2.6	2.6
90°	38.1	38.2	38.5	38.7	39.0	39.2	39.0	38.7	38.5	38.2	38.1
92.5°	36.9	36.9	36.9	36.9	36.9	36.9	36.9	36.9	36.9	36.9	36.9
95°	73.9	73.6	73.1	72.6	72.1	71.6	72.1	72.6	73.1	73.6	73.9
97.5°	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4
100°	159.3	159.2	158.9	158.6	158.4	158.1	158.4	158.6	158.9	159.2	159.3
102.5°	207.8	207.7	207.4	207.1	206.9	206.6	206.9	207.1	207.4	207.7	207.8
105°	256.2	256.2	256.2	256.2	256.2	256.2	256.2	256.2	256.2	256.2	256.2
107.5°	307.0	306.4	305.1	303.8	302.6	301.3	302.6	303.8	305.1	306.4	307.0
110°	359.0	358.6	357.8	357.1	356.3	355.5	356.3	357.1	357.8	358.6	359.0

TEST NUMBER: P1009820

CATALOG NUMBER: S122RDIP-B290D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	409.8	409.5	409.0	408.5	408.0	407.5	408.0	408.5	409.0	409.5	409.8
115°	465.2	464.8	464.0	463.3	462.5	461.7	462.5	463.3	464.0	464.8	465.2
117.5°	516.0	515.6	514.8	514.1	513.3	512.5	513.3	514.1	514.8	515.6	516.0
120°	570.2	569.8	569.0	568.3	567.5	566.7	567.5	568.3	569.0	569.8	570.2
122.5°	622.1	621.8	621.3	620.8	620.3	619.8	620.3	620.8	621.3	621.8	622.1
125°	675.2	675.1	674.8	674.6	674.3	674.1	674.3	674.6	674.8	675.1	675.2
127.5°	726.0	725.6	724.9	724.1	723.4	722.6	723.4	724.1	724.9	725.6	726.0
130°	780.3	779.8	778.8	777.7	776.7	775.7	776.7	777.7	778.8	779.8	780.3
132.5°	829.9	829.5	828.8	828.0	827.3	826.5	827.3	828.0	828.8	829.5	829.9
135°	883.0	882.6	881.8	881.1	880.3	879.5	880.3	881.1	881.8	882.6	883.0
137.5°	931.5	931.0	930.0	928.9	927.9	926.9	927.9	928.9	930.0	931.0	931.5
140°	981.1	980.6	979.6	978.5	977.5	976.5	977.5	978.5	979.6	980.6	981.1
142.5°	1026.1	1025.6	1024.6	1023.5	1022.5	1021.5	1022.5	1023.5	1024.6	1025.6	1026.1
145°	1071.2	1070.7	1069.6	1068.6	1067.5	1066.5	1067.5	1068.6	1069.6	1070.7	1071.2
147.5°	1111.6	1111.1	1110.0	1109.0	1107.9	1106.9	1107.9	1109.0	1110.0	1111.1	1111.6
150°	1149.6	1149.2	1148.5	1147.7	1147.0	1146.2	1147.0	1147.7	1148.5	1149.2	1149.6
152.5°	1187.7	1187.2	1186.2	1185.1	1184.1	1183.1	1184.1	1185.1	1186.2	1187.2	1187.7
155°	1218.9	1218.5	1217.7	1217.0	1216.2	1215.4	1216.2	1217.0	1217.7	1218.5	1218.9
157.5°	1250.1	1249.5	1248.2	1246.9	1245.6	1244.3	1245.6	1246.9	1248.2	1249.5	1250.1
160°	1275.5	1275.0	1273.9	1272.9	1271.8	1270.8	1271.8	1272.9	1273.9	1275.0	1275.5
162.5°	1299.7	1299.1	1297.8	1296.5	1295.2	1293.9	1295.2	1296.5	1297.8	1299.1	1299.7
165°	1319.3	1318.7	1317.4	1316.1	1314.8	1313.5	1314.8	1316.1	1317.4	1318.7	1319.3
167.5°	1336.6	1336.0	1334.7	1333.4	1332.2	1330.9	1332.2	1333.4	1334.7	1336.0	1336.6
170°	1350.5	1349.7	1348.2	1346.7	1345.1	1343.6	1345.1	1346.7	1348.2	1349.7	1350.5
172.5°	1360.9	1360.1	1358.6	1357.0	1355.5	1353.9	1355.5	1357.0	1358.6	1360.1	1360.9
175°	1367.8	1367.0	1365.5	1364.0	1362.4	1360.9	1362.4	1364.0	1365.5	1367.0	1367.8
177.5°	1371.3	1370.5	1369.0	1367.4	1365.9	1364.3	1365.9	1367.4	1369.0	1370.5	1371.3
180°	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8

TEST NUMBER: P1009820

CATALOG NUMBER: S122RDIP-B290D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	602.6	604.8	603.9	599.1	603.9	605.2	607.9	610.5	612.3	614.9	617.1
5°	564.8	569.2	571.8	569.2	578.0	579.3	585.4	589.0	594.2	598.6	602.2
7.5°	529.2	532.7	538.0	538.9	544.1	550.3	559.1	567.9	576.2	580.6	584.6
10°	491.0	497.1	505.0	503.3	511.2	520.8	530.1	544.1	551.2	559.1	566.1
12.5°	452.7	456.7	467.2	470.7	482.2	489.6	502.4	511.2	528.7	538.0	544.1
15°	385.9	402.2	415.4	431.2	446.1	460.2	471.6	487.4	502.8	509.9	520.0
17.5°	355.6	363.0	371.0	378.9	398.2	423.3	443.5	460.6	473.8	483.0	494.9
20°	323.9	331.4	340.2	347.7	359.5	377.6	402.6	432.1	447.9	457.5	469.0
22.5°	301.5	308.5	314.3	320.9	330.1	343.3	362.2	398.6	419.7	431.6	441.7
25°	277.3	286.1	292.3	297.1	304.6	319.1	334.5	355.1	392.9	402.2	416.2
27.5°	260.6	263.3	270.3	277.8	285.3	293.2	309.0	326.6	352.1	372.3	389.4
30°	240.9	247.5	254.0	257.1	263.7	275.1	284.8	303.7	323.5	339.3	360.0
32.5°	225.9	229.9	234.3	241.7	247.9	255.8	265.5	281.3	298.0	308.1	323.9
35°	209.2	211.9	221.1	224.2	230.3	238.2	247.9	260.2	278.2	286.1	297.6
37.5°	193.4	199.5	202.2	209.2	214.9	222.8	229.9	243.9	255.8	265.0	275.6
40°	181.1	183.7	188.6	194.7	199.5	205.7	214.5	224.6	237.3	244.8	254.0
42.5°	166.1	168.3	174.5	178.0	185.9	191.6	196.9	209.2	220.6	226.4	235.6
45°	149.9	155.2	159.1	166.1	170.5	177.6	184.2	193.0	203.5	210.1	215.4
47.5°	135.8	141.1	145.0	151.6	158.7	161.7	168.8	178.0	187.7	193.0	200.4
50°	124.4	126.1	133.6	136.7	144.2	150.3	155.2	163.1	173.6	176.7	182.8
52.5°	113.4	114.7	119.6	123.5	130.1	135.4	141.5	149.0	157.8	162.6	167.5
55°	103.7	104.6	106.8	111.2	115.6	122.2	127.9	134.9	142.4	147.7	152.1
57.5°	92.7	94.5	96.3	98.9	103.3	109.4	115.6	122.2	128.3	131.9	137.6
60°	80.0	82.6	85.7	88.8	91.9	96.3	103.3	109.4	115.2	118.2	122.6
62.5°	66.4	71.6	74.3	77.8	80.4	84.4	89.7	96.7	100.7	104.6	108.1
65°	59.8	60.2	60.7	64.2	69.0	73.0	77.8	83.1	89.2	91.9	94.5
67.5°	53.2	53.6	54.5	54.9	56.7	61.1	66.4	72.1	76.9	78.7	81.3
70°	46.6	46.6	48.3	48.8	49.2	49.7	54.1	59.8	64.2	66.4	69.4
72.5°	39.6	40.0	40.9	41.3	42.2	43.1	44.4	47.5	52.7	54.9	58.5
75°	32.5	33.0	33.4	33.8	35.2	35.6	36.9	38.7	40.9	43.5	45.7
77.5°	25.9	25.9	26.4	27.3	28.1	28.6	29.9	30.8	31.6	33.0	34.7
80°	19.3	19.8	19.8	20.7	20.7	21.1	21.5	22.9	23.7	24.6	25.5
82.5°	13.2	14.1	14.1	14.1	14.5	14.9	15.4	15.4	16.3	16.7	18.0
85°	7.9	8.4	8.4	8.4	7.9	8.8	8.8	9.2	9.2	9.2	9.7
87.5°	3.1	2.6	3.1	3.1	3.1	3.5	3.1	3.1	3.5	4.0	4.0
90°	38.4	38.9	39.4	39.9	40.4	34.8	29.1	23.5	17.8	15.0	13.5
92.5°	36.8	36.5	36.3	36.0	35.8	35.5	35.3	35.0	34.7	34.6	33.6
95°	73.9	73.9	73.9	73.9	73.9	73.4	72.9	72.4	71.9	71.6	70.3
97.5°	115.4	115.4	115.4	115.4	115.4	114.4	113.4	112.3	111.3	110.8	109.6
100°	159.3	159.3	159.3	159.3	159.3	158.5	157.7	157.0	156.2	155.8	154.8
102.5°	207.7	207.4	207.1	206.9	206.6	205.6	204.6	203.5	202.5	202.0	201.2
105°	255.9	255.4	254.9	254.4	253.9	253.4	252.9	252.4	251.9	251.6	251.2
107.5°	306.9	306.6	306.4	306.1	305.9	305.9	305.9	305.9	305.9	305.9	305.4
110°	359.0	359.0	359.0	359.0	359.0	359.0	359.0	359.0	359.0	359.0	358.2

TEST NUMBER: P1009820

CATALOG NUMBER: S122RDIP-B290D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	410.2	410.9	411.7	412.4	413.2	413.5	413.7	414.0	414.3	414.4	413.6
115°	465.3	465.6	465.8	466.1	466.3	466.8	467.3	467.8	468.3	468.6	467.8
117.5°	516.4	517.1	517.9	518.6	519.4	520.7	522.0	523.3	524.6	525.2	524.2
120°	570.2	570.2	570.2	570.2	570.2	572.2	574.3	576.3	578.4	579.4	578.4
122.5°	622.5	623.3	624.0	624.8	625.6	626.9	628.2	629.5	630.8	631.4	630.1
125°	675.6	676.4	677.1	677.9	678.7	679.5	680.3	681.0	681.8	682.2	681.0
127.5°	726.5	727.5	728.6	729.6	730.6	731.6	732.7	733.7	734.8	735.3	733.9
130°	780.6	781.1	781.6	782.1	782.6	783.1	783.6	784.1	784.6	784.9	783.2
132.5°	830.5	831.8	833.1	834.4	835.7	835.4	835.2	834.9	834.6	834.5	833.2
135°	883.1	883.4	883.7	883.9	884.2	883.7	883.2	882.7	882.2	881.9	880.5
137.5°	931.6	931.9	932.1	932.4	932.6	932.1	931.6	931.1	930.6	930.3	929.1
140°	981.1	981.1	981.1	981.1	981.1	979.8	978.6	977.3	976.0	975.4	974.2
142.5°	1026.0	1025.7	1025.5	1025.2	1025.0	1024.2	1023.4	1022.7	1021.9	1021.5	1020.3
145°	1071.1	1070.8	1070.5	1070.3	1070.0	1068.5	1066.9	1065.4	1063.9	1063.1	1062.2
147.5°	1111.3	1110.8	1110.3	1109.7	1109.2	1108.2	1107.2	1106.1	1105.1	1104.6	1103.4
150°	1149.2	1148.5	1147.7	1147.0	1146.2	1145.2	1144.2	1143.1	1142.1	1141.6	1140.8
152.5°	1187.2	1186.2	1185.1	1184.1	1183.1	1181.8	1180.5	1179.2	1177.9	1177.3	1176.5
155°	1218.3	1217.0	1215.7	1214.4	1213.1	1212.3	1211.6	1210.8	1210.1	1209.7	1209.3
157.5°	1249.2	1247.4	1245.6	1243.8	1242.0	1241.5	1241.0	1240.5	1240.0	1239.7	1239.4
160°	1274.7	1273.2	1271.6	1270.1	1268.5	1268.3	1268.0	1267.8	1267.5	1267.4	1267.1
162.5°	1298.8	1297.0	1295.2	1293.4	1291.6	1291.4	1291.1	1290.9	1290.6	1290.5	1290.5
165°	1318.4	1316.6	1314.8	1313.0	1311.2	1311.2	1311.2	1311.2	1311.2	1311.2	1311.3
167.5°	1335.7	1333.9	1332.2	1330.4	1328.6	1328.6	1328.6	1328.6	1328.6	1328.6	1329.0
170°	1349.6	1347.8	1346.0	1344.2	1342.4	1342.7	1342.9	1343.2	1343.5	1343.6	1344.0
172.5°	1360.0	1358.2	1356.4	1354.6	1352.8	1353.0	1353.3	1353.5	1353.8	1353.9	1354.3
175°	1366.9	1365.1	1363.3	1361.5	1359.7	1360.2	1360.7	1361.2	1361.7	1362.0	1362.4
177.5°	1370.5	1369.0	1367.4	1365.9	1364.3	1364.8	1365.3	1365.8	1366.3	1366.6	1367.0
180°	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8	1367.8

TEST NUMBER: P1009820

CATALOG NUMBER: S122RDIP-B290D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	632.5	632.5	632.5	632.5
2.5°	621.1	619.7	627.6	636.4
5°	608.3	610.5	620.6	632.9
7.5°	595.1	600.0	611.8	628.1
10°	576.7	585.4	603.5	620.2
12.5°	558.6	570.5	587.6	607.4
15°	538.4	551.6	572.7	596.4
17.5°	516.0	530.9	555.6	581.5
20°	492.3	512.0	538.0	566.1
22.5°	465.9	489.6	516.4	547.6
25°	440.4	466.3	493.1	529.2
27.5°	415.4	440.8	470.7	507.2
30°	390.3	413.6	445.7	484.8
32.5°	363.5	387.7	421.5	461.5
35°	338.9	363.0	394.7	434.3
37.5°	312.5	338.4	368.8	409.6
40°	281.7	312.1	341.5	380.6
42.5°	256.2	288.3	316.9	353.8
45°	236.0	266.4	290.1	326.1
47.5°	217.1	241.7	265.9	299.3
50°	199.1	218.0	243.1	272.9
52.5°	180.6	196.9	218.4	246.6
55°	163.9	179.3	198.7	220.2
57.5°	148.6	159.5	178.9	198.2
60°	131.4	142.8	157.8	174.1
62.5°	116.9	125.7	139.8	153.4
65°	101.5	109.9	120.4	133.2
67.5°	87.5	94.9	103.3	113.4
70°	74.7	80.4	86.6	95.4
72.5°	61.1	67.2	73.0	80.0
75°	50.1	52.7	57.6	62.4
77.5°	38.7	42.2	44.8	48.8
80°	27.7	30.8	31.6	34.7
82.5°	18.5	20.2	22.0	22.9
85°	10.5	11.4	13.2	13.6
87.5°	4.0	4.4	5.3	6.2
90°	10.4	7.3	4.3	1.2
92.5°	31.5	29.5	27.4	25.4
95°	67.7	65.2	62.6	60.0
97.5°	107.3	105.0	102.7	100.4
100°	152.7	150.7	148.6	146.6
102.5°	199.7	198.2	196.6	195.1
105°	250.5	249.7	249.0	248.2
107.5°	304.4	303.3	302.3	301.3
110°	356.7	355.1	353.6	352.0

TEST NUMBER: P1009820

CATALOG NUMBER: S122RDIP-B290D1080UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	412.1	410.6	409.0	407.5
115°	466.3	464.8	463.2	461.7
117.5°	522.1	520.1	518.0	516.0
120°	576.3	574.3	572.2	570.2
122.5°	627.5	625.0	622.4	619.8
125°	678.7	676.4	674.1	671.8
127.5°	731.1	728.2	725.4	722.6
130°	779.9	776.6	773.2	769.9
132.5°	830.7	828.1	825.6	823.0
135°	877.7	874.8	872.0	869.2
137.5°	926.8	924.5	922.2	919.9
140°	971.9	969.6	967.3	965.0
142.5°	1018.0	1015.7	1013.4	1011.1
145°	1060.4	1058.6	1056.8	1055.0
147.5°	1101.1	1098.8	1096.5	1094.2
150°	1139.3	1137.7	1136.2	1134.6
152.5°	1175.0	1173.5	1171.9	1170.4
155°	1208.5	1207.8	1207.0	1206.2
157.5°	1238.9	1238.4	1237.9	1237.4
160°	1266.6	1266.1	1265.6	1265.1
162.5°	1290.5	1290.5	1290.5	1290.5
165°	1311.6	1311.9	1312.1	1312.4
167.5°	1329.7	1330.5	1331.2	1332.0
170°	1344.7	1345.5	1346.2	1347.0
172.5°	1355.1	1355.8	1356.6	1357.4
175°	1363.2	1363.9	1364.7	1365.5
177.5°	1367.8	1368.5	1369.3	1370.1
180°	1367.8	1367.8	1367.8	1367.8

(END OF REPORT)