

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009892

Luminaire Tested: S122RDIP-B290D725UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009892
REPORT IS A COMBINATION OF REPORTS P988140 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B290D725UB27-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3833.0 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009892

CATALOG NUMBER: S122RDIP-B290D725UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1009892

CATALOG NUMBER: S122RDIP-B290D725UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	86	83	84	80	77	75	63	61	59	47	46	45	33	32	31
2	85	79	73	68	76	71	66	62	56	53	50	42	40	38	29	28	27
3	78	69	63	57	70	63	57	52	50	46	42	38	35	33	26	25	24
4	72	62	54	49	64	56	49	45	44	40	36	34	31	29	24	22	21
5	66	55	48	42	59	50	43	38	40	35	32	31	27	25	22	20	18
6	61	49	42	36	54	45	38	34	36	31	28	28	25	22	20	18	17
7	56	45	37	32	50	41	34	30	33	28	25	25	22	20	18	16	15
8	52	41	33	28	47	37	31	26	30	25	22	23	20	18	17	15	13
9	49	37	30	25	44	34	28	23	27	23	20	21	18	16	16	14	12
10	45	34	27	23	41	31	25	21	25	21	18	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9984	9984	9984	9984
5°	10008	10604	10043	8472
10°	9898	11209	9968	6996
15°	9683	11212	9847	5256
20°	9425	9268	9629	4336
25°	9110	5791	9307	3688
30°	8712	3709	8948	3175
35°	8225	2850	8491	2718
40°	7683	2395	8011	2377
45°	7102	2038	7399	1996
50°	6509	1733	6813	1726
55°	5851	1506	6166	1486
60°	5268	1148	5547	1134
65°	4721	865	5002	980
70°	4119	690	4443	798
75°	3479	528	3798	605
80°	2762	359	2978	395
85°	1921	186	2105	195

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 9134 cd/sqm

TEST NUMBER: P1009892

CATALOG NUMBER: S122RDIP-B290D725UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.8	1.6
10°-20°	167.0	4.4
20°-30°	214.9	5.6
30°-40°	203.9	5.3
40°-50°	174.7	4.6
50°-60°	133.1	3.5
60°-70°	83.9	2.2
70°-80°	41.9	1.1
80°-90°	13.3	0.3
90°-100°	153.4	4.0
100°-110°	540.2	14.1
110°-120°	567.4	14.8
120°-130°	466.8	12.2
130°-140°	375.0	9.8
140°-150°	283.2	7.4
150°-160°	199.1	5.2
160°-170°	117.2	3.1
170°-180°	38.1	1.0
0°-30°	441.7	11.5
0°-40°	645.6	16.8
0°-60°	953.4	24.9
0°-90°	1092.5	28.5
90°-120°	1261.0	32.9
90°-150°	2386.0	62.2
90°-180°	2740.0	71.5
0°-180°	3833.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	631	631	631	631	631	
5°	631	702	633	561	631	60
15°	595	792	605	371	595	167
25°	528	422	539	269	528	242
35°	433	208	447	199	433	271
45°	325	145	339	142	325	251
55°	220	100	231	99	220	198
65°	133	52	141	59	133	132
75°	62	28	68	32	62	67
85°	14	8	15	8	14	15
90°	1	25	1	25	1	3
95°	26	86	26	86	26	27
105°	92	853	92	853	92	98
115°	163	1122	163	1122	163	161
125°	227	910	227	910	227	202
135°	266	754	266	754	266	206
145°	304	602	304	602	304	191
155°	346	506	346	506	346	159
165°	377	444	377	444	377	106
175°	393	400	393	400	393	37
180°	394	394	394	394	394	

TEST NUMBER: P1009892

CATALOG NUMBER: S122RDIP-B290D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	634.7	637.3	638.6	640.4	644.3	647.0	650.9	651.8	651.3	653.1	648.3
5°	631.2	636.9	642.1	646.5	653.5	657.9	662.7	668.4	669.8	676.3	672.4
7.5°	626.4	634.7	642.1	650.9	661.4	667.1	674.6	683.3	687.3	695.2	697.4
10°	618.5	630.3	643.0	652.2	666.7	676.8	683.8	697.8	707.0	718.8	717.1
12.5°	605.8	621.1	638.2	653.5	672.4	679.0	692.1	706.6	718.4	729.4	739.0
15°	594.8	612.3	631.2	650.0	671.5	683.8	696.9	715.8	728.5	747.8	756.1
17.5°	579.9	602.3	624.6	645.6	671.1	685.1	701.3	719.7	738.6	757.0	763.6
20°	564.6	588.7	612.8	641.3	670.2	683.8	700.4	723.2	741.6	756.1	756.1
22.5°	546.1	575.5	603.1	630.3	661.9	681.6	698.7	725.4	738.6	741.6	729.8
25°	527.7	557.1	587.3	621.1	657.0	674.6	693.9	718.8	723.2	711.0	680.3
27.5°	505.8	538.7	572.9	609.3	647.0	668.9	686.4	703.1	694.7	661.9	614.1
30°	483.5	519.0	557.5	592.2	637.8	657.9	672.8	677.6	651.3	597.9	536.1
32.5°	460.2	494.9	535.6	577.3	623.3	642.6	652.2	639.5	591.3	523.8	448.4
35°	433.1	472.1	514.6	558.0	603.6	618.0	623.7	592.6	530.8	443.6	368.6
37.5°	408.5	447.5	493.1	537.4	581.6	589.5	583.8	535.2	456.7	370.4	297.2
40°	379.6	421.2	465.9	515.5	551.8	554.0	540.0	476.9	379.6	298.5	253.3
42.5°	352.8	394.9	439.6	490.0	517.7	510.2	491.4	408.5	316.9	257.3	220.9
45°	325.2	365.1	413.3	458.0	477.8	460.2	431.7	343.6	266.1	221.4	193.3
47.5°	298.5	335.8	383.5	426.5	430.0	410.3	376.5	288.0	230.6	194.6	171.8
50°	272.2	309.5	354.2	389.7	386.2	359.0	320.8	250.3	200.3	171.8	153.0
52.5°	245.9	279.6	323.0	351.1	336.2	309.9	272.2	212.1	174.9	149.9	135.4
55°	219.6	251.2	288.4	311.6	288.0	257.7	231.0	181.9	151.7	131.5	120.5
57.5°	197.7	222.7	256.9	270.9	242.4	218.7	195.5	156.5	131.5	117.0	104.3
60°	173.6	196.4	224.4	232.7	203.4	184.1	164.4	132.4	112.6	99.9	91.6
62.5°	153.0	171.8	193.3	193.3	167.4	153.0	138.1	110.9	94.7	84.6	80.7
65°	132.8	146.4	161.7	160.0	138.1	125.4	113.5	91.6	79.3	72.3	68.4
67.5°	113.1	123.6	133.7	127.6	111.8	100.8	89.9	74.1	65.7	60.9	55.7
70°	95.1	103.4	108.7	103.0	87.2	78.0	70.1	59.6	53.0	46.9	43.8
72.5°	79.8	83.3	85.0	78.0	64.9	59.6	53.9	46.5	40.8	37.7	36.8
75°	62.2	65.3	64.0	58.7	47.8	43.8	39.4	34.2	32.9	31.1	30.2
77.5°	48.7	48.7	46.5	41.6	34.2	31.1	29.4	26.7	25.4	25.0	24.1
80°	34.6	34.2	32.9	27.6	23.2	21.5	21.5	19.7	19.3	18.4	18.4
82.5°	22.8	22.8	21.0	16.7	15.3	14.9	14.5	13.6	13.6	13.1	13.1
85°	13.6	12.7	10.5	9.2	8.8	8.8	8.3	7.9	8.3	7.9	7.9
87.5°	6.1	4.8	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
90°	0.8	3.0	6.1	7.6	9.1	10.2	11.4	15.1	20.4	25.0	25.7
92.5°	11.4	15.9	21.9	25.7	31.8	36.0	40.1	60.5	89.3	115.0	116.5
95°	26.5	29.5	37.1	43.9	56.0	65.1	74.2	109.0	174.8	262.6	296.7
97.5°	39.4	43.9	52.2	62.1	75.7	85.9	96.1	140.8	232.3	373.8	483.6
100°	58.3	60.5	67.4	79.5	94.6	105.2	115.8	155.9	248.2	411.7	597.8
102.5°	75.7	77.2	84.0	96.1	112.0	122.6	133.2	169.5	249.0	397.3	601.6
105°	92.3	95.4	100.6	112.0	128.7	139.2	149.8	185.4	252.8	377.6	560.8
107.5°	110.5	112.8	118.1	128.7	145.3	155.9	166.5	201.3	261.1	367.0	522.9
110°	128.7	131.7	136.2	146.1	161.9	172.9	183.9	217.2	271.7	364.0	497.2

TEST NUMBER: P1009892

CATALOG NUMBER: S122RDIP-B290D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	145.3	148.3	153.6	162.7	177.8	189.2	200.5	232.3	283.0	364.8	480.5
115°	162.7	166.5	171.0	180.1	195.2	205.4	215.7	248.2	294.4	367.8	469.2
117.5°	180.9	183.9	188.4	196.8	211.1	221.7	232.3	262.6	306.5	372.3	463.1
120°	197.5	200.5	205.1	211.9	227.0	237.6	248.2	277.7	318.6	376.9	457.8
122.5°	213.4	215.7	220.2	227.8	242.9	253.9	264.9	292.1	329.2	382.2	454.8
125°	227.0	229.3	233.8	242.9	258.1	268.6	279.2	306.5	340.5	387.5	451.0
127.5°	238.4	241.4	247.5	257.3	271.7	282.6	293.6	320.1	351.1	392.8	448.8
130°	248.2	251.2	258.8	269.4	284.5	295.1	305.7	332.2	361.0	398.8	447.2
132.5°	257.3	261.1	269.4	280.8	296.7	307.2	317.8	342.8	370.8	404.9	446.5
135°	266.4	269.4	278.5	289.8	307.2	317.8	328.4	352.7	379.1	409.4	445.7
137.5°	274.7	278.5	287.6	299.7	317.1	327.0	336.8	361.0	386.0	414.0	445.7
140°	284.5	287.6	296.7	308.8	325.4	335.2	345.1	367.8	391.2	417.0	445.0
142.5°	294.4	296.7	305.0	317.1	333.0	342.0	351.1	373.1	395.8	419.2	445.0
145°	304.2	307.2	314.8	326.2	341.3	349.6	358.0	378.4	399.6	420.8	443.5
147.5°	314.8	317.1	324.7	335.2	348.1	355.6	363.2	382.9	401.8	421.5	441.2
150°	325.4	327.7	333.7	343.6	354.9	361.7	368.5	386.0	403.4	420.8	438.9
152.5°	336.0	336.8	342.8	351.1	361.7	367.8	373.8	389.0	404.1	419.2	435.1
155°	345.8	346.6	351.1	359.5	367.8	373.5	379.1	392.0	404.9	417.7	430.6
157.5°	354.2	354.9	358.7	366.3	373.1	378.0	382.9	394.3	404.9	414.7	426.1
160°	362.5	363.2	366.3	372.3	378.4	382.5	386.7	395.8	404.9	412.4	421.5
162.5°	370.8	370.1	373.1	377.6	382.9	386.0	389.0	396.5	404.1	410.2	417.7
165°	376.9	376.1	377.6	382.2	386.0	388.2	390.5	397.3	402.6	407.1	412.4
167.5°	382.2	381.4	382.9	386.0	389.0	390.5	392.0	397.3	401.8	404.1	407.9
170°	387.5	386.0	386.7	389.0	390.5	391.6	392.8	396.5	400.3	401.8	404.1
172.5°	390.5	389.7	389.0	391.2	392.0	392.8	393.5	395.8	398.1	398.8	399.6
175°	392.8	392.0	391.2	392.8	392.8	393.2	393.5	395.0	396.5	395.8	396.5
177.5°	394.3	392.8	392.0	393.5	393.5	393.5	393.5	394.3	395.8	394.3	393.5
180°	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5

TEST NUMBER: P1009892

CATALOG NUMBER: S122RDIP-B290D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	653.1	654.0	655.3	661.4	662.3	664.1	663.2	663.2	663.6	662.7	663.2
5°	681.1	682.5	689.0	696.5	698.2	696.5	698.7	701.7	701.7	701.7	700.9
7.5°	707.4	712.3	719.7	730.7	732.9	735.1	739.0	736.4	737.3	741.2	739.9
10°	732.9	739.9	748.2	757.4	762.2	765.3	767.1	771.0	780.2	769.7	773.6
12.5°	757.0	767.1	775.8	785.9	789.4	793.4	794.7	798.2	798.2	797.7	800.8
15°	772.8	782.0	789.9	796.4	797.3	796.4	795.5	796.0	797.3	792.0	795.1
17.5°	776.3	777.1	779.8	777.1	777.6	768.4	763.1	761.8	749.5	750.0	760.0
20°	759.2	744.3	740.3	725.9	717.1	693.4	692.5	686.0	660.1	668.0	666.2
22.5°	712.3	686.8	653.1	636.4	628.1	603.1	583.8	570.3	561.0	551.8	547.9
25°	650.5	609.3	561.5	528.6	523.8	500.6	465.1	448.4	428.7	422.5	433.1
27.5°	570.7	517.2	463.3	412.9	403.7	382.7	364.7	352.8	330.1	328.7	329.6
30°	462.4	408.5	363.4	330.5	307.7	298.1	286.2	277.5	268.3	271.8	272.6
32.5°	380.0	328.7	286.7	269.1	258.6	252.5	242.4	236.7	232.7	231.4	231.0
35°	302.0	267.8	249.0	231.9	225.7	221.4	213.9	211.3	207.8	208.2	208.2
37.5°	258.6	230.1	216.1	207.3	201.6	199.4	194.6	192.0	189.8	188.9	190.2
40°	223.1	203.4	194.6	186.7	181.9	181.0	178.4	175.3	172.7	173.1	174.5
42.5°	197.2	185.8	175.3	169.2	165.7	164.4	162.2	160.0	160.0	158.7	158.2
45°	176.6	167.4	158.7	153.0	150.8	149.0	146.4	146.0	144.2	144.6	145.1
47.5°	158.2	150.8	144.2	138.5	136.3	135.9	133.2	131.5	131.5	131.1	130.6
50°	141.6	134.1	128.4	125.4	122.3	121.4	121.0	120.5	119.7	119.7	120.1
52.5°	128.0	120.5	116.2	113.5	111.8	110.9	110.9	110.5	110.5	110.5	110.0
55°	113.1	106.9	103.4	102.6	101.7	101.3	100.8	99.9	99.5	100.4	99.5
57.5°	99.1	96.9	93.8	92.9	90.7	90.7	89.4	88.5	87.7	88.5	88.5
60°	88.1	85.0	83.3	80.7	78.9	77.1	75.0	74.5	73.6	73.2	72.8
62.5°	76.7	74.1	69.7	65.7	63.1	61.4	60.5	60.0	60.0	59.6	59.6
65°	64.0	57.9	55.7	54.4	53.9	53.5	52.6	52.2	52.6	52.2	52.6
67.5°	50.0	49.1	47.8	46.9	46.5	46.0	46.0	45.6	45.6	45.6	45.6
70°	43.4	41.2	40.8	39.9	39.9	39.4	39.4	39.4	39.4	39.0	39.9
72.5°	35.9	34.6	34.2	33.8	33.8	33.8	33.3	33.3	33.3	32.9	33.3
75°	29.4	28.9	28.1	28.1	27.6	28.1	27.6	27.6	27.2	27.6	27.6
77.5°	23.7	23.2	22.8	22.8	22.4	22.4	22.4	22.4	22.4	22.4	22.8
80°	18.0	17.5	17.1	17.5	17.1	17.5	17.1	17.1	17.5	17.1	17.1
82.5°	13.1	12.7	12.7	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3
85°	7.9	7.5	7.5	7.9	7.5	7.9	7.5	7.5	7.5	7.9	7.9
87.5°	3.5	3.9	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.9
90°	25.0	24.2	22.7	24.2	24.6	25.0	25.0	25.0	25.0	25.0	25.0
92.5°	97.6	76.4	65.1	56.8	53.8	50.7	49.9	46.9	47.7	46.2	47.7
95°	259.6	198.3	152.1	120.3	112.0	103.7	93.8	87.8	85.5	86.3	85.5
97.5°	487.4	405.6	323.9	247.5	224.8	202.1	172.5	157.4	149.1	144.5	149.1
100°	706.8	690.9	597.1	493.4	447.6	401.8	339.0	306.5	284.5	270.9	284.5
102.5°	788.5	877.8	874.8	806.0	756.8	707.6	638.0	576.7	547.9	528.2	547.9
105°	762.1	919.5	1005.0	1014.8	1002.3	989.8	942.9	896.0	863.5	852.9	863.5
107.5°	706.1	874.8	1002.0	1076.1	1091.2	1106.4	1105.6	1098.8	1089.0	1071.6	1089.0
110°	653.8	813.5	949.0	1045.9	1076.9	1107.9	1140.4	1154.8	1161.6	1160.9	1161.6

TEST NUMBER: P1009892

CATALOG NUMBER: S122RDIP-B290D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	617.5	757.5	886.2	991.4	1028.1	1064.8	1113.2	1139.7	1154.1	1159.4	1154.1
115°	588.8	713.6	830.2	929.3	968.3	1007.3	1061.0	1095.8	1115.5	1122.3	1115.5
117.5°	569.1	677.3	781.7	874.1	911.2	948.2	1003.5	1040.6	1061.0	1066.3	1061.0
120°	554.0	651.6	745.4	825.6	860.0	894.5	947.5	983.0	1005.0	1012.6	1005.0
122.5°	541.1	631.1	715.1	790.1	820.4	850.6	896.8	931.6	950.5	956.6	950.5
125°	529.0	611.5	689.4	756.0	784.4	812.8	856.7	885.4	904.3	910.4	904.3
127.5°	517.6	591.8	663.7	727.3	753.8	780.2	818.8	846.1	862.7	867.3	862.7
130°	506.3	572.9	638.0	697.7	722.7	747.7	784.8	810.5	825.6	831.7	825.6
132.5°	497.2	554.7	613.7	667.5	690.6	713.6	750.0	775.7	789.3	794.6	789.3
135°	488.9	538.1	588.0	638.0	659.2	680.3	712.9	737.8	751.5	754.5	751.5
137.5°	482.8	524.4	567.6	608.4	627.3	646.3	677.3	699.3	711.4	715.9	711.4
140°	477.5	511.6	547.9	582.7	599.4	616.0	640.2	659.9	671.3	675.8	671.3
142.5°	472.2	501.0	530.5	559.2	572.4	585.7	608.4	625.8	635.7	635.7	635.7
145°	467.7	491.1	516.1	539.6	550.6	561.5	579.7	592.5	600.1	602.4	600.1
147.5°	463.1	483.6	504.0	522.9	531.2	539.6	555.5	566.1	571.4	572.9	571.4
150°	457.1	475.2	491.9	507.8	514.6	521.4	532.8	541.8	546.4	547.1	546.4
152.5°	451.8	466.9	482.1	494.9	500.6	506.3	514.6	522.2	525.2	525.2	525.2
155°	445.0	459.4	471.5	482.8	487.0	491.1	499.5	504.8	507.8	506.3	507.8
157.5°	438.9	450.3	460.9	470.7	474.1	477.5	483.6	488.1	489.6	489.6	489.6
160°	432.1	442.0	450.3	458.6	461.2	463.9	469.2	473.0	473.7	473.7	473.7
162.5°	426.1	433.6	440.4	447.2	449.1	451.0	456.3	458.6	459.4	458.6	459.4
165°	419.2	425.3	430.6	435.9	437.4	438.9	442.0	445.0	445.0	444.2	445.0
167.5°	412.4	417.0	421.5	425.3	426.8	428.3	429.8	431.4	431.4	430.6	431.4
170°	407.1	410.9	413.2	416.2	417.0	417.7	418.5	420.8	420.0	418.5	420.0
172.5°	401.8	404.1	405.6	407.9	408.3	408.7	409.4	410.2	409.4	408.7	409.4
175°	397.3	399.6	400.3	401.1	401.5	401.8	401.8	402.6	401.8	400.3	401.8
177.5°	394.3	395.8	395.8	396.5	396.5	396.5	396.5	396.5	395.8	394.3	395.8
180°	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5

TEST NUMBER: P1009892

CATALOG NUMBER: S122RDIP-B290D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	664.9	661.9	661.0	661.9	661.0	661.4	658.4	647.0	650.0	645.2	647.8
5°	702.6	700.0	694.3	693.4	692.5	691.7	687.3	677.2	673.3	666.7	666.2
7.5°	738.6	738.6	734.2	731.1	727.2	724.1	718.4	703.5	697.4	689.5	685.1
10°	774.1	762.7	767.5	764.4	754.8	753.0	742.5	733.7	721.9	714.0	707.0
12.5°	799.5	796.0	791.6	789.0	786.3	780.6	773.6	751.3	745.1	729.4	721.5
15°	798.6	796.4	797.7	797.7	796.9	795.5	789.9	773.6	763.1	747.8	734.2
17.5°	755.7	761.4	767.1	771.0	779.8	783.7	789.0	779.3	772.8	759.6	745.1
20°	680.7	694.7	711.4	714.9	722.8	746.0	756.5	764.9	767.5	763.1	751.3
22.5°	576.4	588.2	628.6	627.7	639.1	666.7	697.4	722.4	742.1	753.0	748.6
25°	451.5	468.1	489.6	505.8	543.1	584.3	622.4	662.3	696.5	726.7	734.2
27.5°	341.5	363.4	380.5	401.9	420.8	469.4	518.5	580.8	620.7	678.1	707.9
30°	276.1	286.2	303.3	313.4	322.6	359.9	415.5	476.9	547.0	613.2	664.5
32.5°	235.8	242.8	255.5	259.9	269.6	294.6	329.6	385.7	458.0	538.3	605.8
35°	211.7	219.2	221.8	225.7	233.6	249.4	273.5	314.3	379.6	458.0	538.7
37.5°	191.1	195.1	202.5	205.1	207.8	219.6	235.8	264.3	307.7	372.1	461.6
40°	176.6	178.8	182.8	185.0	186.7	195.1	209.5	228.8	260.8	309.9	392.3
42.5°	161.3	163.9	166.6	169.2	171.4	178.0	186.7	205.1	226.6	263.9	323.5
45°	146.4	148.2	151.2	153.0	156.0	161.3	169.2	181.9	201.2	224.9	273.1
47.5°	132.8	135.0	136.3	138.5	140.7	146.4	153.9	162.2	178.0	201.2	236.3
50°	120.5	123.2	124.9	125.4	127.1	132.4	138.5	147.7	157.8	175.8	206.4
52.5°	111.8	112.2	113.5	115.3	114.8	117.9	123.6	130.6	141.1	155.6	178.0
55°	101.7	103.0	103.9	104.3	104.3	106.9	110.0	116.6	124.9	136.8	155.6
57.5°	89.0	90.3	92.9	93.8	95.1	96.4	97.7	102.1	109.1	120.5	135.9
60°	75.8	76.7	79.3	81.1	82.0	85.5	87.2	90.7	94.7	103.0	117.5
62.5°	60.9	61.8	63.1	64.9	66.6	71.9	76.3	79.8	82.8	88.5	100.4
65°	53.0	53.5	54.4	54.8	55.2	57.4	61.4	66.2	71.9	76.3	83.3
67.5°	46.0	46.5	46.9	47.8	48.2	48.7	50.4	51.7	57.4	63.6	68.8
70°	39.4	40.3	40.8	40.8	41.2	42.1	43.0	44.7	46.5	49.5	56.1
72.5°	33.3	33.8	34.6	34.6	34.6	35.5	36.4	37.3	38.1	39.9	42.5
75°	27.6	28.5	28.5	28.5	28.9	28.9	29.8	30.7	31.6	32.9	33.8
77.5°	22.8	22.8	22.8	22.8	23.2	23.2	23.7	24.5	25.0	25.4	26.3
80°	17.1	17.5	17.5	17.5	18.0	18.0	18.0	18.8	19.3	19.3	20.2
82.5°	12.7	12.7	12.7	13.1	12.7	13.1	13.1	13.6	13.1	13.6	14.0
85°	7.9	7.9	7.9	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.8
87.5°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	4.4	3.9	3.9
90°	25.0	25.0	25.0	24.6	24.2	22.7	24.2	25.0	25.7	25.0	20.4
92.5°	46.9	49.9	50.7	53.8	56.8	65.1	76.4	97.6	116.5	115.0	89.3
95°	87.8	93.8	103.7	112.0	120.3	152.1	198.3	259.6	296.7	262.6	174.8
97.5°	157.4	172.5	202.1	224.8	247.5	323.9	405.6	487.4	483.6	373.8	232.3
100°	306.5	339.0	401.8	447.6	493.4	597.1	690.9	706.8	597.8	411.7	248.2
102.5°	576.7	638.0	707.6	756.8	806.0	874.8	877.8	788.5	601.6	397.3	249.0
105°	896.0	942.9	989.8	1002.3	1014.8	1005.0	919.5	762.1	560.8	377.6	252.8
107.5°	1098.8	1105.6	1106.4	1091.2	1076.1	1002.0	874.8	706.1	522.9	367.0	261.1
110°	1154.8	1140.4	1107.9	1076.9	1045.9	949.0	813.5	653.8	497.2	364.0	271.7

TEST NUMBER: P1009892

CATALOG NUMBER: S122RDIP-B290D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1139.7	1113.2	1064.8	1028.1	991.4	886.2	757.5	617.5	480.5	364.8	283.0
115°	1095.8	1061.0	1007.3	968.3	929.3	830.2	713.6	588.8	469.2	367.8	294.4
117.5°	1040.6	1003.5	948.2	911.2	874.1	781.7	677.3	569.1	463.1	372.3	306.5
120°	983.0	947.5	894.5	860.0	825.6	745.4	651.6	554.0	457.8	376.9	318.6
122.5°	931.6	896.8	850.6	820.4	790.1	715.1	631.1	541.1	454.8	382.2	329.2
125°	885.4	856.7	812.8	784.4	756.0	689.4	611.5	529.0	451.0	387.5	340.5
127.5°	846.1	818.8	780.2	753.8	727.3	663.7	591.8	517.6	448.8	392.8	351.1
130°	810.5	784.8	747.7	722.7	697.7	638.0	572.9	506.3	447.2	398.8	361.0
132.5°	775.7	750.0	713.6	690.6	667.5	613.7	554.7	497.2	446.5	404.9	370.8
135°	737.8	712.9	680.3	659.2	638.0	588.0	538.1	488.9	445.7	409.4	379.1
137.5°	699.3	677.3	646.3	627.3	608.4	567.6	524.4	482.8	445.7	414.0	386.0
140°	659.9	640.2	616.0	599.4	582.7	547.9	511.6	477.5	445.0	417.0	391.2
142.5°	625.8	608.4	585.7	572.4	559.2	530.5	501.0	472.2	445.0	419.2	395.8
145°	592.5	579.7	561.5	550.6	539.6	516.1	491.1	467.7	443.5	420.8	399.6
147.5°	566.1	555.5	539.6	531.2	522.9	504.0	483.6	463.1	441.2	421.5	401.8
150°	541.8	532.8	521.4	514.6	507.8	491.9	475.2	457.1	438.9	420.8	403.4
152.5°	522.2	514.6	506.3	500.6	494.9	482.1	466.9	451.8	435.1	419.2	404.1
155°	504.8	499.5	491.1	487.0	482.8	471.5	459.4	445.0	430.6	417.7	404.9
157.5°	488.1	483.6	477.5	474.1	470.7	460.9	450.3	438.9	426.1	414.7	404.9
160°	473.0	469.2	463.9	461.2	458.6	450.3	442.0	432.1	421.5	412.4	404.9
162.5°	458.6	456.3	451.0	449.1	447.2	440.4	433.6	426.1	417.7	410.2	404.1
165°	445.0	442.0	438.9	437.4	435.9	430.6	425.3	419.2	412.4	407.1	402.6
167.5°	431.4	429.8	428.3	426.8	425.3	421.5	417.0	412.4	407.9	404.1	401.8
170°	420.8	418.5	417.7	417.0	416.2	413.2	410.9	407.1	404.1	401.8	400.3
172.5°	410.2	409.4	408.7	408.3	407.9	405.6	404.1	401.8	399.6	398.8	398.1
175°	402.6	401.8	401.8	401.5	401.1	400.3	399.6	397.3	396.5	395.8	396.5
177.5°	396.5	396.5	396.5	396.5	396.5	395.8	395.8	394.3	393.5	394.3	395.8
180°	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5

TEST NUMBER: P1009892

CATALOG NUMBER: S122RDIP-B290D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	643.9	641.7	641.7	640.4	640.4	633.4	633.4	635.6	632.9	629.9	625.5
5°	660.5	655.7	654.4	652.7	647.0	638.2	634.7	633.4	628.1	621.5	614.1
7.5°	676.3	668.4	664.5	660.5	653.1	640.8	633.8	629.0	621.1	611.0	601.4
10°	691.7	681.6	671.5	666.7	656.2	640.8	630.7	622.9	611.5	597.9	584.3
12.5°	705.7	684.7	682.9	673.3	657.9	640.4	625.0	613.6	599.2	583.4	567.6
15°	718.0	696.5	686.0	677.2	657.0	635.1	618.9	604.9	585.6	567.6	548.3
17.5°	724.1	700.9	693.9	679.4	658.8	630.3	608.4	591.3	570.3	548.8	526.9
20°	730.2	703.1	691.7	681.6	653.5	621.1	596.6	576.8	553.6	528.2	504.1
22.5°	733.3	703.1	689.5	675.5	648.3	611.0	582.1	558.9	531.7	505.8	476.9
25°	728.0	700.4	684.2	669.8	639.1	598.7	565.4	539.1	510.2	480.8	451.5
27.5°	714.9	694.3	675.5	660.5	626.4	583.0	547.9	518.1	488.3	455.4	425.6
30°	690.4	681.1	666.2	649.6	612.3	568.9	527.3	496.6	463.7	430.9	399.7
32.5°	652.2	660.1	650.5	636.0	595.7	549.7	505.4	474.3	438.3	402.8	374.3
35°	605.8	633.8	628.6	618.5	578.1	529.1	484.8	447.1	411.1	375.2	346.7
37.5°	554.9	597.4	601.8	595.7	558.0	508.0	459.4	422.5	385.7	349.3	320.4
40°	485.2	550.5	564.6	567.2	536.9	482.6	431.7	395.8	359.4	323.9	288.9
42.5°	421.2	503.6	521.2	532.1	510.2	457.6	406.3	366.4	330.5	298.5	263.4
45°	361.2	447.1	475.6	489.6	480.0	429.1	376.1	338.8	305.9	276.6	242.8
47.5°	299.4	385.7	425.6	448.0	448.0	400.2	347.1	310.3	278.8	253.8	224.0
50°	258.2	330.1	371.3	400.6	408.5	370.8	320.8	284.9	255.1	227.9	205.1
52.5°	220.0	284.5	318.7	349.3	372.1	339.3	291.5	259.0	229.7	204.3	186.3
55°	190.2	238.4	269.6	303.3	328.7	307.3	263.0	231.4	206.0	185.0	169.6
57.5°	161.7	203.8	229.2	259.0	286.2	270.0	234.5	207.3	185.0	166.6	153.0
60°	137.6	171.8	191.5	214.8	248.5	237.1	207.8	182.8	164.8	148.2	136.8
62.5°	117.0	144.2	160.9	177.5	208.2	202.9	180.1	160.9	145.5	131.5	121.9
65°	96.0	118.3	131.5	146.0	170.5	172.7	154.3	140.7	126.7	114.4	105.6
67.5°	77.6	95.1	106.9	119.2	138.9	145.1	132.4	121.0	109.1	99.1	91.2
70°	62.7	75.0	83.7	93.4	109.6	117.0	110.5	102.6	92.9	84.6	77.6
72.5°	49.5	57.4	62.7	70.1	83.3	90.7	90.3	83.3	76.3	70.6	64.9
75°	36.4	42.5	46.9	51.7	62.2	69.3	71.0	67.9	60.9	56.5	52.2
77.5°	27.6	31.1	33.3	36.8	44.3	50.4	53.0	52.2	47.3	43.8	40.8
80°	21.0	21.9	22.8	24.1	30.2	35.9	37.7	37.3	34.6	33.3	29.8
82.5°	14.9	15.3	15.8	16.2	18.4	23.2	25.0	25.9	23.7	22.4	19.3
85°	8.8	9.2	9.2	10.1	10.5	11.8	14.9	14.9	14.5	12.7	12.3
87.5°	4.4	4.4	3.9	3.9	4.4	4.8	5.7	6.6	5.7	5.3	4.8
90°	15.1	11.4	10.2	9.1	7.6	6.1	3.0	0.8	3.0	6.1	7.6
92.5°	60.5	40.1	36.0	31.8	25.7	21.9	15.9	11.4	15.9	21.9	25.7
95°	109.0	74.2	65.1	56.0	43.9	37.1	29.5	26.5	29.5	37.1	43.9
97.5°	140.8	96.1	85.9	75.7	62.1	52.2	43.9	39.4	43.9	52.2	62.1
100°	155.9	115.8	105.2	94.6	79.5	67.4	60.5	58.3	60.5	67.4	79.5
102.5°	169.5	133.2	122.6	112.0	96.1	84.0	77.2	75.7	77.2	84.0	96.1
105°	185.4	149.8	139.2	128.7	112.0	100.6	95.4	92.3	95.4	100.6	112.0
107.5°	201.3	166.5	155.9	145.3	128.7	118.1	112.8	110.5	112.8	118.1	128.7
110°	217.2	183.9	172.9	161.9	146.1	136.2	131.7	128.7	131.7	136.2	146.1

TEST NUMBER: P1009892

CATALOG NUMBER: S122RDIP-B290D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	232.3	200.5	189.2	177.8	162.7	153.6	148.3	145.3	148.3	153.6	162.7
115°	248.2	215.7	205.4	195.2	180.1	171.0	166.5	162.7	166.5	171.0	180.1
117.5°	262.6	232.3	221.7	211.1	196.8	188.4	183.9	180.9	183.9	188.4	196.8
120°	277.7	248.2	237.6	227.0	211.9	205.1	200.5	197.5	200.5	205.1	211.9
122.5°	292.1	264.9	253.9	242.9	227.8	220.2	215.7	213.4	215.7	220.2	227.8
125°	306.5	279.2	268.6	258.1	242.9	233.8	229.3	227.0	229.3	233.8	242.9
127.5°	320.1	293.6	282.6	271.7	257.3	247.5	241.4	238.4	241.4	247.5	257.3
130°	332.2	305.7	295.1	284.5	269.4	258.8	251.2	248.2	251.2	258.8	269.4
132.5°	342.8	317.8	307.2	296.7	280.8	269.4	261.1	257.3	261.1	269.4	280.8
135°	352.7	328.4	317.8	307.2	289.8	278.5	269.4	266.4	269.4	278.5	289.8
137.5°	361.0	336.8	327.0	317.1	299.7	287.6	278.5	274.7	278.5	287.6	299.7
140°	367.8	345.1	335.2	325.4	308.8	296.7	287.6	284.5	287.6	296.7	308.8
142.5°	373.1	351.1	342.0	333.0	317.1	305.0	296.7	294.4	296.7	305.0	317.1
145°	378.4	358.0	349.6	341.3	326.2	314.8	307.2	304.2	307.2	314.8	326.2
147.5°	382.9	363.2	355.6	348.1	335.2	324.7	317.1	314.8	317.1	324.7	335.2
150°	386.0	368.5	361.7	354.9	343.6	333.7	327.7	325.4	327.7	333.7	343.6
152.5°	389.0	373.8	367.8	361.7	351.1	342.8	336.8	336.0	336.8	342.8	351.1
155°	392.0	379.1	373.5	367.8	359.5	351.1	346.6	345.8	346.6	351.1	359.5
157.5°	394.3	382.9	378.0	373.1	366.3	358.7	354.9	354.2	354.9	358.7	366.3
160°	395.8	386.7	382.5	378.4	372.3	366.3	363.2	362.5	363.2	366.3	372.3
162.5°	396.5	389.0	386.0	382.9	377.6	373.1	370.1	370.8	370.1	373.1	377.6
165°	397.3	390.5	388.2	386.0	382.2	377.6	376.1	376.9	376.1	377.6	382.2
167.5°	397.3	392.0	390.5	389.0	386.0	382.9	381.4	382.2	381.4	382.9	386.0
170°	396.5	392.8	391.6	390.5	389.0	386.7	386.0	387.5	386.0	386.7	389.0
172.5°	395.8	393.5	392.8	392.0	391.2	389.0	389.7	390.5	389.7	389.0	391.2
175°	395.0	393.5	393.2	392.8	392.8	391.2	392.0	392.8	392.0	391.2	392.8
177.5°	394.3	393.5	393.5	393.5	393.5	392.0	392.8	394.3	392.8	392.0	393.5
180°	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5

TEST NUMBER: P1009892

CATALOG NUMBER: S122RDIP-B290D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	623.7	624.2	625.5	621.5	615.4	612.8	604.9	603.6	602.3	602.3	603.6
5°	609.7	607.9	608.4	600.9	592.2	586.9	576.0	577.7	572.0	568.5	569.4
7.5°	594.4	589.5	589.1	579.5	568.5	558.9	547.5	544.8	539.6	533.4	530.8
10°	575.1	571.6	565.0	554.0	540.0	532.1	516.8	507.6	506.3	497.1	493.5
12.5°	555.4	549.2	542.6	527.3	511.5	498.8	487.4	477.3	470.3	462.4	457.2
15°	532.6	525.1	517.7	501.4	483.0	470.3	453.2	438.3	417.7	401.5	392.3
17.5°	507.6	499.2	489.2	471.2	453.2	435.7	404.1	386.6	372.1	362.5	356.8
20°	481.7	472.5	462.4	444.5	413.3	382.7	365.1	351.5	342.8	333.1	326.1
22.5°	454.5	444.9	433.9	405.9	373.0	351.5	337.9	325.2	312.5	307.3	303.8
25°	429.1	420.3	406.3	368.2	342.3	322.6	307.3	298.9	292.4	285.3	278.8
27.5°	402.8	386.6	366.9	334.9	318.7	298.5	287.5	281.4	270.0	265.2	262.1
30°	371.3	353.3	334.4	311.6	292.8	278.8	268.7	258.6	252.0	247.2	242.0
32.5°	339.3	322.2	310.3	286.7	272.6	258.2	248.5	242.4	232.7	229.7	227.5
35°	311.6	297.2	286.7	267.4	254.2	241.1	234.1	224.9	218.7	213.0	209.5
37.5°	284.5	276.6	265.6	249.4	235.4	224.9	215.2	212.1	203.8	200.8	197.2
40°	265.6	253.8	244.6	230.6	218.7	207.3	201.2	194.2	188.5	183.7	182.3
42.5°	242.8	234.1	228.8	213.5	201.2	194.6	187.2	179.3	174.9	170.9	166.1
45°	225.7	217.8	210.4	198.1	187.2	178.8	172.3	167.0	159.5	157.8	150.3
47.5°	207.8	199.9	194.2	181.9	171.8	163.9	159.1	152.1	146.0	142.0	138.5
50°	189.8	183.2	178.0	167.4	158.7	150.3	143.8	136.8	134.1	127.6	125.4
52.5°	172.7	168.3	162.6	152.5	143.8	136.8	129.7	124.0	120.1	116.6	114.0
55°	158.2	151.2	148.6	137.6	130.2	122.7	116.6	113.1	108.3	106.1	103.9
57.5°	142.0	138.1	133.7	125.4	117.0	110.0	105.6	100.4	97.7	95.1	93.4
60°	128.0	122.3	118.8	111.8	104.3	97.7	93.8	89.9	86.3	84.2	80.7
62.5°	111.8	107.4	105.2	97.7	91.6	85.5	82.0	78.0	75.4	71.4	67.1
65°	97.7	94.2	91.6	85.5	79.8	74.1	70.6	65.7	62.2	60.0	59.6
67.5°	85.5	82.8	78.9	73.2	67.5	63.1	59.2	55.2	54.8	53.9	53.9
70°	71.9	69.3	67.1	60.9	56.1	51.3	50.4	49.1	47.8	47.3	46.5
72.5°	60.0	57.9	55.2	50.0	45.1	43.8	43.0	42.1	40.8	40.3	39.9
75°	48.7	45.6	43.8	39.0	37.7	36.8	35.9	34.6	33.8	33.3	32.4
77.5°	37.3	34.2	34.2	31.6	30.7	29.4	28.5	27.6	27.2	26.3	26.3
80°	26.3	26.3	25.4	24.1	22.8	22.4	21.0	20.6	20.2	20.6	19.7
82.5°	19.3	17.5	17.5	16.7	15.8	15.3	14.5	14.5	14.0	14.0	14.0
85°	11.0	11.0	10.5	9.6	9.2	9.2	8.8	8.8	8.3	8.3	7.9
87.5°	4.4	3.9	4.4	3.9	3.9	3.5	3.5	3.5	3.1	3.5	3.1
90°	9.1	10.2	11.4	15.1	20.4	25.0	25.7	25.0	24.2	22.7	24.2
92.5°	31.8	36.0	40.1	60.5	89.3	115.0	116.5	97.6	76.4	65.1	56.8
95°	56.0	65.1	74.2	109.0	174.8	262.6	296.7	259.6	198.3	152.1	120.3
97.5°	75.7	85.9	96.1	140.8	232.3	373.8	483.6	487.4	405.6	323.9	247.5
100°	94.6	105.2	115.8	155.9	248.2	411.7	597.8	706.8	690.9	597.1	493.4
102.5°	112.0	122.6	133.2	169.5	249.0	397.3	601.6	788.5	877.8	874.8	806.0
105°	128.7	139.2	149.8	185.4	252.8	377.6	560.8	762.1	919.5	1005.0	1014.8
107.5°	145.3	155.9	166.5	201.3	261.1	367.0	522.9	706.1	874.8	1002.0	1076.1
110°	161.9	172.9	183.9	217.2	271.7	364.0	497.2	653.8	813.5	949.0	1045.9

TEST NUMBER: P1009892

CATALOG NUMBER: S122RDIP-B290D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	177.8	189.2	200.5	232.3	283.0	364.8	480.5	617.5	757.5	886.2	991.4
115°	195.2	205.4	215.7	248.2	294.4	367.8	469.2	588.8	713.6	830.2	929.3
117.5°	211.1	221.7	232.3	262.6	306.5	372.3	463.1	569.1	677.3	781.7	874.1
120°	227.0	237.6	248.2	277.7	318.6	376.9	457.8	554.0	651.6	745.4	825.6
122.5°	242.9	253.9	264.9	292.1	329.2	382.2	454.8	541.1	631.1	715.1	790.1
125°	258.1	268.6	279.2	306.5	340.5	387.5	451.0	529.0	611.5	689.4	756.0
127.5°	271.7	282.6	293.6	320.1	351.1	392.8	448.8	517.6	591.8	663.7	727.3
130°	284.5	295.1	305.7	332.2	361.0	398.8	447.2	506.3	572.9	638.0	697.7
132.5°	296.7	307.2	317.8	342.8	370.8	404.9	446.5	497.2	554.7	613.7	667.5
135°	307.2	317.8	328.4	352.7	379.1	409.4	445.7	488.9	538.1	588.0	638.0
137.5°	317.1	327.0	336.8	361.0	386.0	414.0	445.7	482.8	524.4	567.6	608.4
140°	325.4	335.2	345.1	367.8	391.2	417.0	445.0	477.5	511.6	547.9	582.7
142.5°	333.0	342.0	351.1	373.1	395.8	419.2	445.0	472.2	501.0	530.5	559.2
145°	341.3	349.6	358.0	378.4	399.6	420.8	443.5	467.7	491.1	516.1	539.6
147.5°	348.1	355.6	363.2	382.9	401.8	421.5	441.2	463.1	483.6	504.0	522.9
150°	354.9	361.7	368.5	386.0	403.4	420.8	438.9	457.1	475.2	491.9	507.8
152.5°	361.7	367.8	373.8	389.0	404.1	419.2	435.1	451.8	466.9	482.1	494.9
155°	367.8	373.5	379.1	392.0	404.9	417.7	430.6	445.0	459.4	471.5	482.8
157.5°	373.1	378.0	382.9	394.3	404.9	414.7	426.1	438.9	450.3	460.9	470.7
160°	378.4	382.5	386.7	395.8	404.9	412.4	421.5	432.1	442.0	450.3	458.6
162.5°	382.9	386.0	389.0	396.5	404.1	410.2	417.7	426.1	433.6	440.4	447.2
165°	386.0	388.2	390.5	397.3	402.6	407.1	412.4	419.2	425.3	430.6	435.9
167.5°	389.0	390.5	392.0	397.3	401.8	404.1	407.9	412.4	417.0	421.5	425.3
170°	390.5	391.6	392.8	396.5	400.3	401.8	404.1	407.1	410.9	413.2	416.2
172.5°	392.0	392.8	393.5	395.8	398.1	398.8	399.6	401.8	404.1	405.6	407.9
175°	392.8	393.2	393.5	395.0	396.5	395.8	396.5	397.3	399.6	400.3	401.1
177.5°	393.5	393.5	393.5	394.3	395.8	394.3	393.5	394.3	395.8	395.8	396.5
180°	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5

TEST NUMBER: P1009892

CATALOG NUMBER: S122RDIP-B290D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	603.6	602.7	600.1	600.9	599.6	599.6	598.7	598.7	598.7	600.9	599.6
5°	570.7	567.6	564.6	563.2	561.9	560.6	560.6	560.2	564.1	563.2	566.7
7.5°	529.9	529.1	522.9	522.9	520.7	519.8	522.0	522.5	522.9	523.8	526.0
10°	493.5	491.4	482.6	483.5	482.2	480.4	481.7	480.8	483.9	484.8	483.9
12.5°	450.6	446.6	437.0	432.2	426.9	423.0	427.8	424.3	436.6	440.1	449.7
15°	393.6	386.2	379.6	379.6	374.8	371.3	373.4	377.4	380.0	384.0	385.7
17.5°	355.5	352.4	347.1	344.1	342.8	341.5	341.5	343.2	348.9	348.5	352.0
20°	323.0	321.3	318.7	314.7	313.4	312.5	312.5	312.5	316.5	320.0	322.2
22.5°	300.7	299.4	297.6	292.4	289.7	288.9	291.0	292.4	295.4	298.1	300.2
25°	278.3	275.3	272.2	270.4	269.1	269.1	270.0	270.4	271.8	273.1	275.7
27.5°	259.9	257.7	253.3	248.5	248.5	247.2	248.1	249.0	252.0	256.4	258.6
30°	239.3	238.9	237.1	235.4	233.6	232.7	234.5	235.8	236.3	238.4	238.4
32.5°	224.4	221.4	218.3	216.5	215.7	215.2	215.7	217.4	217.4	220.0	223.1
35°	209.5	207.8	204.7	201.6	200.8	198.6	200.3	202.1	205.1	206.4	207.8
37.5°	193.3	191.1	189.8	188.9	187.2	187.6	186.3	188.9	191.5	191.1	192.0
40°	181.0	177.1	173.1	172.7	172.3	171.8	171.8	172.3	174.0	175.8	178.4
42.5°	165.2	163.9	160.4	156.9	156.0	155.2	154.3	156.0	159.5	162.6	163.9
45°	149.0	147.3	146.4	143.8	142.0	141.6	140.7	142.9	146.0	147.3	148.2
47.5°	134.1	133.7	131.1	131.5	130.2	130.6	130.2	131.5	131.5	132.8	133.7
50°	124.0	122.7	121.4	120.5	119.2	119.2	118.8	119.2	121.0	122.7	122.3
52.5°	114.0	111.8	111.3	110.9	110.0	110.9	109.6	110.0	111.8	112.6	112.2
55°	102.1	101.7	100.8	99.9	99.5	99.1	99.1	99.1	100.8	102.1	102.6
57.5°	92.9	90.7	89.0	89.0	87.2	86.8	87.7	88.1	89.4	90.3	91.2
60°	80.2	79.3	76.7	75.4	72.8	72.3	72.3	74.1	76.3	79.3	80.2
62.5°	66.6	65.3	64.9	64.9	64.9	64.9	64.9	64.9	64.9	65.3	65.3
65°	59.2	59.6	59.2	58.7	59.2	59.2	58.7	58.7	58.7	59.2	59.6
67.5°	53.0	52.6	53.0	52.6	52.2	52.2	51.7	52.2	52.6	53.0	53.0
70°	46.0	46.0	45.6	46.0	45.6	45.1	44.7	44.7	45.6	46.0	46.0
72.5°	39.4	39.4	39.0	39.0	38.1	38.1	38.6	38.1	38.1	39.4	39.4
75°	32.9	32.4	32.0	32.0	31.6	31.6	31.6	31.1	32.0	32.0	32.4
77.5°	25.9	25.9	25.9	25.4	25.4	25.0	25.0	25.4	25.4	25.4	25.9
80°	19.7	19.7	19.7	19.3	18.8	18.8	18.8	18.8	18.8	19.3	18.8
82.5°	13.6	13.6	13.6	13.6	13.6	13.1	13.1	13.1	13.6	13.6	13.1
85°	8.3	7.9	8.3	8.3	7.9	8.3	7.9	7.9	7.5	7.5	7.9
87.5°	3.5	3.1	2.6	2.6	3.1	2.6	2.6	2.6	3.1	2.6	2.6
90°	24.6	25.0	25.0	25.0	25.0	25.0	25.0	25.0	25.0	25.0	24.6
92.5°	53.8	50.7	49.9	46.9	47.7	46.2	47.7	46.9	49.9	50.7	53.8
95°	112.0	103.7	93.8	87.8	85.5	86.3	85.5	87.8	93.8	103.7	112.0
97.5°	224.8	202.1	172.5	157.4	149.1	144.5	149.1	157.4	172.5	202.1	224.8
100°	447.6	401.8	339.0	306.5	284.5	270.9	284.5	306.5	339.0	401.8	447.6
102.5°	756.8	707.6	638.0	576.7	547.9	528.2	547.9	576.7	638.0	707.6	756.8
105°	1002.3	989.8	942.9	896.0	863.5	852.9	863.5	896.0	942.9	989.8	1002.3
107.5°	1091.2	1106.4	1105.6	1098.8	1089.0	1071.6	1089.0	1098.8	1105.6	1106.4	1091.2
110°	1076.9	1107.9	1140.4	1154.8	1161.6	1160.9	1161.6	1154.8	1140.4	1107.9	1076.9

TEST NUMBER: P1009892

CATALOG NUMBER: S122RDIP-B290D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1028.1	1064.8	1113.2	1139.7	1154.1	1159.4	1154.1	1139.7	1113.2	1064.8	1028.1
115°	968.3	1007.3	1061.0	1095.8	1115.5	1122.3	1115.5	1095.8	1061.0	1007.3	968.3
117.5°	911.2	948.2	1003.5	1040.6	1061.0	1066.3	1061.0	1040.6	1003.5	948.2	911.2
120°	860.0	894.5	947.5	983.0	1005.0	1012.6	1005.0	983.0	947.5	894.5	860.0
122.5°	820.4	850.6	896.8	931.6	950.5	956.6	950.5	931.6	896.8	850.6	820.4
125°	784.4	812.8	856.7	885.4	904.3	910.4	904.3	885.4	856.7	812.8	784.4
127.5°	753.8	780.2	818.8	846.1	862.7	867.3	862.7	846.1	818.8	780.2	753.8
130°	722.7	747.7	784.8	810.5	825.6	831.7	825.6	810.5	784.8	747.7	722.7
132.5°	690.6	713.6	750.0	775.7	789.3	794.6	789.3	775.7	750.0	713.6	690.6
135°	659.2	680.3	712.9	737.8	751.5	754.5	751.5	737.8	712.9	680.3	659.2
137.5°	627.3	646.3	677.3	699.3	711.4	715.9	711.4	699.3	677.3	646.3	627.3
140°	599.4	616.0	640.2	659.9	671.3	675.8	671.3	659.9	640.2	616.0	599.4
142.5°	572.4	585.7	608.4	625.8	635.7	635.7	635.7	625.8	608.4	585.7	572.4
145°	550.6	561.5	579.7	592.5	600.1	602.4	600.1	592.5	579.7	561.5	550.6
147.5°	531.2	539.6	555.5	566.1	571.4	572.9	571.4	566.1	555.5	539.6	531.2
150°	514.6	521.4	532.8	541.8	546.4	547.1	546.4	541.8	532.8	521.4	514.6
152.5°	500.6	506.3	514.6	522.2	525.2	525.2	525.2	522.2	514.6	506.3	500.6
155°	487.0	491.1	499.5	504.8	507.8	506.3	507.8	504.8	499.5	491.1	487.0
157.5°	474.1	477.5	483.6	488.1	489.6	489.6	489.6	488.1	483.6	477.5	474.1
160°	461.2	463.9	469.2	473.0	473.7	473.7	473.7	473.0	469.2	463.9	461.2
162.5°	449.1	451.0	456.3	458.6	459.4	458.6	459.4	458.6	456.3	451.0	449.1
165°	437.4	438.9	442.0	445.0	445.0	444.2	445.0	445.0	442.0	438.9	437.4
167.5°	426.8	428.3	429.8	431.4	431.4	430.6	431.4	431.4	429.8	428.3	426.8
170°	417.0	417.7	418.5	420.8	420.0	418.5	420.0	420.8	418.5	417.7	417.0
172.5°	408.3	408.7	409.4	410.2	409.4	408.7	409.4	410.2	409.4	408.7	408.3
175°	401.5	401.8	401.8	402.6	401.8	400.3	401.8	402.6	401.8	401.8	401.5
177.5°	396.5	396.5	396.5	396.5	395.8	394.3	395.8	396.5	396.5	396.5	396.5
180°	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5

TEST NUMBER: P1009892

CATALOG NUMBER: S122RDIP-B290D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	600.9	603.1	602.3	597.4	602.3	603.6	606.2	608.8	610.6	613.2	615.4
5°	563.2	567.6	570.3	567.6	576.4	577.7	583.8	587.3	592.6	597.0	600.5
7.5°	527.7	531.2	536.5	537.4	542.6	548.8	557.5	566.3	574.6	579.0	583.0
10°	489.6	495.7	503.6	501.9	509.8	519.4	528.6	542.6	549.7	557.5	564.6
12.5°	451.5	455.4	465.9	469.4	480.8	488.3	501.0	509.8	527.3	536.5	542.6
15°	384.8	401.1	414.2	430.0	444.9	458.9	470.3	486.1	501.4	508.5	518.5
17.5°	354.6	362.1	369.9	377.8	397.1	422.1	442.3	459.4	472.5	481.7	493.5
20°	323.0	330.5	339.3	346.7	358.5	376.5	401.5	430.9	446.6	456.3	467.7
22.5°	300.7	307.7	313.4	320.0	329.2	342.3	361.2	397.6	418.6	430.4	440.5
25°	276.6	285.3	291.5	296.3	303.8	318.2	333.6	354.2	391.9	401.1	415.1
27.5°	259.9	262.6	269.6	277.0	284.5	292.4	308.1	325.7	351.1	371.3	388.4
30°	240.2	246.8	253.3	256.4	263.0	274.4	284.0	302.9	322.6	338.4	359.0
32.5°	225.3	229.2	233.6	241.1	247.2	255.1	264.7	280.5	297.2	307.3	323.0
35°	208.6	211.3	220.5	223.5	229.7	237.6	247.2	259.5	277.5	285.3	296.7
37.5°	192.9	199.0	201.6	208.6	214.3	222.2	229.2	243.3	255.1	264.3	274.8
40°	180.6	183.2	188.0	194.2	199.0	205.1	213.9	224.0	236.7	244.1	253.3
42.5°	165.7	167.9	174.0	177.5	185.4	191.1	196.4	208.6	220.0	225.7	234.9
45°	149.5	154.7	158.7	165.7	170.1	177.1	183.7	192.4	202.9	209.5	214.8
47.5°	135.4	140.7	144.6	151.2	158.2	161.3	168.3	177.5	187.2	192.4	199.9
50°	124.0	125.8	133.2	136.3	143.8	149.9	154.7	162.6	173.1	176.2	182.3
52.5°	113.1	114.4	119.2	123.2	129.7	135.0	141.1	148.6	157.4	162.2	167.0
55°	103.4	104.3	106.5	110.9	115.3	121.9	127.6	134.6	142.0	147.3	151.7
57.5°	92.5	94.2	96.0	98.6	103.0	109.1	115.3	121.9	128.0	131.5	137.2
60°	79.8	82.4	85.5	88.5	91.6	96.0	103.0	109.1	114.8	117.9	122.3
62.5°	66.2	71.4	74.1	77.6	80.2	84.2	89.4	96.4	100.4	104.3	107.8
65°	59.6	60.0	60.5	64.0	68.8	72.8	77.6	82.8	89.0	91.6	94.2
67.5°	53.0	53.5	54.4	54.8	56.5	60.9	66.2	71.9	76.7	78.5	81.1
70°	46.5	46.5	48.2	48.7	49.1	49.5	53.9	59.6	64.0	66.2	69.3
72.5°	39.4	39.9	40.8	41.2	42.1	43.0	44.3	47.3	52.6	54.8	58.3
75°	32.4	32.9	33.3	33.8	35.1	35.5	36.8	38.6	40.8	43.4	45.6
77.5°	25.9	25.9	26.3	27.2	28.1	28.5	29.8	30.7	31.6	32.9	34.6
80°	19.3	19.7	19.7	20.6	20.6	21.0	21.5	22.8	23.7	24.5	25.4
82.5°	13.1	14.0	14.0	14.0	14.5	14.9	15.3	15.3	16.2	16.7	18.0
85°	7.9	8.3	8.3	8.3	7.9	8.8	8.8	9.2	9.2	9.2	9.6
87.5°	3.1	2.6	3.1	3.1	3.1	3.5	3.1	3.1	3.5	3.9	3.9
90°	24.2	22.7	24.2	25.0	25.7	25.0	20.4	15.1	11.4	10.2	9.1
92.5°	56.8	65.1	76.4	97.6	116.5	115.0	89.3	60.5	40.1	36.0	31.8
95°	120.3	152.1	198.3	259.6	296.7	262.6	174.8	109.0	74.2	65.1	56.0
97.5°	247.5	323.9	405.6	487.4	483.6	373.8	232.3	140.8	96.1	85.9	75.7
100°	493.4	597.1	690.9	706.8	597.8	411.7	248.2	155.9	115.8	105.2	94.6
102.5°	806.0	874.8	877.8	788.5	601.6	397.3	249.0	169.5	133.2	122.6	112.0
105°	1014.8	1005.0	919.5	762.1	560.8	377.6	252.8	185.4	149.8	139.2	128.7
107.5°	1076.1	1002.0	874.8	706.1	522.9	367.0	261.1	201.3	166.5	155.9	145.3
110°	1045.9	949.0	813.5	653.8	497.2	364.0	271.7	217.2	183.9	172.9	161.9

TEST NUMBER: P1009892

CATALOG NUMBER: S122RDIP-B290D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	991.4	886.2	757.5	617.5	480.5	364.8	283.0	232.3	200.5	189.2	177.8
115°	929.3	830.2	713.6	588.8	469.2	367.8	294.4	248.2	215.7	205.4	195.2
117.5°	874.1	781.7	677.3	569.1	463.1	372.3	306.5	262.6	232.3	221.7	211.1
120°	825.6	745.4	651.6	554.0	457.8	376.9	318.6	277.7	248.2	237.6	227.0
122.5°	790.1	715.1	631.1	541.1	454.8	382.2	329.2	292.1	264.9	253.9	242.9
125°	756.0	689.4	611.5	529.0	451.0	387.5	340.5	306.5	279.2	268.6	258.1
127.5°	727.3	663.7	591.8	517.6	448.8	392.8	351.1	320.1	293.6	282.6	271.7
130°	697.7	638.0	572.9	506.3	447.2	398.8	361.0	332.2	305.7	295.1	284.5
132.5°	667.5	613.7	554.7	497.2	446.5	404.9	370.8	342.8	317.8	307.2	296.7
135°	638.0	588.0	538.1	488.9	445.7	409.4	379.1	352.7	328.4	317.8	307.2
137.5°	608.4	567.6	524.4	482.8	445.7	414.0	386.0	361.0	336.8	327.0	317.1
140°	582.7	547.9	511.6	477.5	445.0	417.0	391.2	367.8	345.1	335.2	325.4
142.5°	559.2	530.5	501.0	472.2	445.0	419.2	395.8	373.1	351.1	342.0	333.0
145°	539.6	516.1	491.1	467.7	443.5	420.8	399.6	378.4	358.0	349.6	341.3
147.5°	522.9	504.0	483.6	463.1	441.2	421.5	401.8	382.9	363.2	355.6	348.1
150°	507.8	491.9	475.2	457.1	438.9	420.8	403.4	386.0	368.5	361.7	354.9
152.5°	494.9	482.1	466.9	451.8	435.1	419.2	404.1	389.0	373.8	367.8	361.7
155°	482.8	471.5	459.4	445.0	430.6	417.7	404.9	392.0	379.1	373.5	367.8
157.5°	470.7	460.9	450.3	438.9	426.1	414.7	404.9	394.3	382.9	378.0	373.1
160°	458.6	450.3	442.0	432.1	421.5	412.4	404.9	395.8	386.7	382.5	378.4
162.5°	447.2	440.4	433.6	426.1	417.7	410.2	404.1	396.5	389.0	386.0	382.9
165°	435.9	430.6	425.3	419.2	412.4	407.1	402.6	397.3	390.5	388.2	386.0
167.5°	425.3	421.5	417.0	412.4	407.9	404.1	401.8	397.3	392.0	390.5	389.0
170°	416.2	413.2	410.9	407.1	404.1	401.8	400.3	396.5	392.8	391.6	390.5
172.5°	407.9	405.6	404.1	401.8	399.6	398.8	398.1	395.8	393.5	392.8	392.0
175°	401.1	400.3	399.6	397.3	396.5	395.8	396.5	395.0	393.5	393.2	392.8
177.5°	396.5	395.8	395.8	394.3	393.5	394.3	395.8	394.3	393.5	393.5	393.5
180°	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5

TEST NUMBER: P1009892

CATALOG NUMBER: S122RDIP-B290D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	630.7	630.7	630.7	630.7
2.5°	619.3	618.0	625.9	634.7
5°	606.6	608.8	618.9	631.2
7.5°	593.5	598.3	610.1	626.4
10°	575.1	583.8	601.8	618.5
12.5°	557.1	568.9	586.0	605.8
15°	536.9	550.1	571.1	594.8
17.5°	514.6	529.5	554.0	579.9
20°	490.9	510.6	536.5	564.6
22.5°	464.6	488.3	515.0	546.1
25°	439.2	465.1	491.8	527.7
27.5°	414.2	439.6	469.4	505.8
30°	389.2	412.5	444.5	483.5
32.5°	362.5	386.6	420.3	460.2
35°	337.9	362.1	393.6	433.1
37.5°	311.6	337.5	367.8	408.5
40°	281.0	311.2	340.6	379.6
42.5°	255.5	287.5	316.0	352.8
45°	235.4	265.6	289.3	325.2
47.5°	216.5	241.1	265.2	298.5
50°	198.6	217.4	242.4	272.2
52.5°	180.1	196.4	217.8	245.9
55°	163.5	178.8	198.1	219.6
57.5°	148.2	159.1	178.4	197.7
60°	131.1	142.5	157.4	173.6
62.5°	116.6	125.4	139.4	153.0
65°	101.3	109.6	120.1	132.8
67.5°	87.2	94.7	103.0	113.1
70°	74.5	80.2	86.3	95.1
72.5°	60.9	67.1	72.8	79.8
75°	50.0	52.6	57.4	62.2
77.5°	38.6	42.1	44.7	48.7
80°	27.6	30.7	31.6	34.6
82.5°	18.4	20.2	21.9	22.8
85°	10.5	11.4	13.1	13.6
87.5°	3.9	4.4	5.3	6.1
90°	7.6	6.1	3.0	0.8
92.5°	25.7	21.9	15.9	11.4
95°	43.9	37.1	29.5	26.5
97.5°	62.1	52.2	43.9	39.4
100°	79.5	67.4	60.5	58.3
102.5°	96.1	84.0	77.2	75.7
105°	112.0	100.6	95.4	92.3
107.5°	128.7	118.1	112.8	110.5
110°	146.1	136.2	131.7	128.7

TEST NUMBER: P1009892

CATALOG NUMBER: S122RDIP-B290D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	162.7	153.6	148.3	145.3
115°	180.1	171.0	166.5	162.7
117.5°	196.8	188.4	183.9	180.9
120°	211.9	205.1	200.5	197.5
122.5°	227.8	220.2	215.7	213.4
125°	242.9	233.8	229.3	227.0
127.5°	257.3	247.5	241.4	238.4
130°	269.4	258.8	251.2	248.2
132.5°	280.8	269.4	261.1	257.3
135°	289.8	278.5	269.4	266.4
137.5°	299.7	287.6	278.5	274.7
140°	308.8	296.7	287.6	284.5
142.5°	317.1	305.0	296.7	294.4
145°	326.2	314.8	307.2	304.2
147.5°	335.2	324.7	317.1	314.8
150°	343.6	333.7	327.7	325.4
152.5°	351.1	342.8	336.8	336.0
155°	359.5	351.1	346.6	345.8
157.5°	366.3	358.7	354.9	354.2
160°	372.3	366.3	363.2	362.5
162.5°	377.6	373.1	370.1	370.8
165°	382.2	377.6	376.1	376.9
167.5°	386.0	382.9	381.4	382.2
170°	389.0	386.7	386.0	387.5
172.5°	391.2	389.0	389.7	390.5
175°	392.8	391.2	392.0	392.8
177.5°	393.5	392.0	392.8	394.3
180°	393.5	393.5	393.5	393.5

(END OF REPORT)