

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009897

Luminaire Tested: S122RDIP-B290D725UB30-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009897
REPORT IS A COMBINATION OF REPORTS P988155 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B290D725UB30-4F0-XX-W2A-A1
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3632.0 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009897

CATALOG NUMBER: S122RDIP-B290D725UB30-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1009897

CATALOG NUMBER: S122RDIP-B290D725UB30-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	55	55	55	38	38	38
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	34	34	33
2	86	79	73	69	77	71	66	62	57	53	51	43	41	39	31	30	29
3	79	70	63	58	70	63	57	53	50	46	43	39	36	34	28	26	25
4	72	62	55	49	65	56	50	45	45	41	37	35	32	29	25	23	22
5	66	55	48	42	59	50	44	39	41	36	32	31	28	26	23	21	19
6	61	50	42	37	55	45	39	34	37	32	28	29	25	23	21	19	17
7	57	45	38	32	51	41	35	30	33	29	25	26	23	20	19	17	16
8	53	41	34	29	47	37	31	27	30	26	22	24	21	18	18	16	14
9	49	37	30	26	44	34	28	24	28	23	20	22	19	17	17	14	13
10	46	34	28	23	41	31	25	21	26	21	18	20	17	15	15	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10075	10075	10075	10075
5°	10100	10702	10135	8550
10°	9987	11313	10059	7060
15°	9772	11315	9936	5304
20°	9510	9353	9717	4376
25°	9195	5844	9394	3723
30°	8791	3743	9031	3205
35°	8299	2876	8569	2743
40°	7754	2417	8083	2399
45°	7168	2058	7467	2014
50°	6569	1749	6875	1742
55°	5905	1519	6225	1500
60°	5316	1159	5599	1145
65°	4764	871	5048	989
70°	4157	697	4482	807
75°	3513	534	3838	609
80°	2786	364	3002	399
85°	1935	188	2119	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 9218 cd/sqm

TEST NUMBER: P1009897

CATALOG NUMBER: S122RDIP-B290D725UB30-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.4	1.7
10°-20°	168.5	4.6
20°-30°	216.9	6.0
30°-40°	205.8	5.7
40°-50°	176.3	4.9
50°-60°	134.3	3.7
60°-70°	84.7	2.3
70°-80°	42.3	1.2
80°-90°	13.4	0.4
90°-100°	56.0	1.5
100°-110°	177.9	4.9
110°-120°	304.4	8.4
120°-130°	400.4	11.0
130°-140°	449.4	12.4
140°-150°	440.7	12.1
150°-160°	369.7	10.2
160°-170°	245.2	6.8
170°-180°	85.7	2.4
0°-30°	445.8	12.3
0°-40°	651.5	17.9
0°-60°	962.2	26.5
0°-90°	1102.6	30.4
90°-120°	538.3	14.8
90°-150°	1828.9	50.4
90°-180°	2529.0	69.6
0°-180°	3632.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	636	636	636	636	636	
5°	637	708	639	566	637	60
15°	600	799	610	375	600	169
25°	533	426	544	272	533	245
35°	437	210	451	200	437	273
45°	328	146	342	143	328	253
55°	222	101	234	100	222	200
65°	134	53	142	60	134	133
75°	63	28	69	32	63	68
85°	14	8	15	8	14	16
90°	1	26	1	26	1	3
95°	40	47	40	47	40	44
105°	164	170	164	170	164	173
115°	305	305	305	305	305	302
125°	444	446	444	446	444	397
135°	575	582	575	582	575	444
145°	698	706	698	706	698	436
155°	798	804	798	804	798	367
165°	868	869	868	869	868	245
175°	903	900	903	900	903	86
180°	905	905	905	905	905	

TEST NUMBER: P1009897

CATALOG NUMBER: S122RDIP-B290D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5
2.5°	640.5	643.2	644.5	646.3	650.2	652.9	656.9	657.8	657.3	659.1	654.2
5°	637.0	642.7	648.0	652.5	659.5	664.0	668.8	674.6	675.9	682.5	678.6
7.5°	632.1	640.5	648.0	656.9	667.5	673.2	680.8	689.6	693.6	701.6	703.8
10°	624.1	636.1	648.9	658.2	672.8	683.0	690.1	704.2	713.5	725.4	723.7
12.5°	611.3	626.8	644.0	659.5	678.6	685.2	698.5	713.1	725.0	736.1	745.8
15°	600.3	618.0	637.0	656.0	677.7	690.1	703.3	722.3	735.2	754.6	763.0
17.5°	585.2	607.8	630.3	651.6	677.2	691.4	707.7	726.3	745.3	763.9	770.6
20°	569.7	594.1	618.4	647.1	676.3	690.1	706.9	729.9	748.4	763.0	763.0
22.5°	551.2	580.8	608.7	636.1	667.9	687.8	705.1	732.1	745.3	748.4	736.5
25°	532.6	562.2	592.7	626.8	663.1	680.8	700.2	725.4	729.9	717.5	686.5
27.5°	510.5	543.6	578.1	614.9	652.9	675.0	692.7	709.5	701.1	667.9	619.7
30°	487.9	523.7	562.7	597.6	643.6	664.0	679.0	683.9	657.3	603.4	541.0
32.5°	464.5	499.4	540.5	582.6	629.0	648.5	658.2	645.4	596.7	528.6	452.5
35°	437.0	476.4	519.3	563.1	609.1	623.7	629.5	598.0	535.7	447.6	372.0
37.5°	412.3	451.6	497.6	542.3	587.0	594.9	589.2	540.1	460.9	373.8	299.9
40°	383.1	425.1	470.2	520.2	556.9	559.1	545.0	481.3	383.1	301.2	255.7
42.5°	356.1	398.5	443.7	494.5	522.4	514.9	495.9	412.3	319.8	259.7	222.9
45°	328.2	368.5	417.1	462.2	482.2	464.5	435.7	346.8	268.5	223.4	195.1
47.5°	301.2	338.8	387.0	430.4	433.9	414.0	380.0	290.6	232.7	196.4	173.4
50°	274.7	312.3	357.4	393.2	389.7	362.3	323.8	252.6	202.1	173.4	154.4
52.5°	248.2	282.2	326.0	354.3	339.3	312.7	274.7	214.1	176.5	151.3	136.7
55°	221.6	253.5	291.1	314.5	290.6	260.1	233.1	183.6	153.0	132.7	121.6
57.5°	199.5	224.7	259.2	273.4	244.6	220.7	197.3	157.9	132.7	118.1	105.3
60°	175.2	198.2	226.5	234.9	205.2	185.8	165.9	133.6	113.7	100.9	92.4
62.5°	154.4	173.4	195.1	195.1	169.0	154.4	139.3	111.9	95.5	85.4	81.4
65°	134.0	147.7	163.2	161.5	139.3	126.5	114.6	92.4	80.1	73.0	69.0
67.5°	114.1	124.7	134.9	128.7	112.8	101.7	90.7	74.8	66.4	61.5	56.2
70°	96.0	104.4	109.7	104.0	88.0	78.7	70.8	60.2	53.5	47.3	44.2
72.5°	80.5	84.0	85.8	78.7	65.5	60.2	54.4	46.9	41.1	38.0	37.2
75°	62.8	65.9	64.6	59.3	48.2	44.2	39.8	34.5	33.2	31.4	30.5
77.5°	49.1	49.1	46.9	42.0	34.5	31.4	29.6	27.0	25.7	25.2	24.3
80°	34.9	34.5	33.2	27.9	23.4	21.7	21.7	19.9	19.5	18.6	18.6
82.5°	23.0	23.0	21.2	16.8	15.5	15.0	14.6	13.7	13.7	13.3	13.3
85°	13.7	12.8	10.6	9.3	8.8	8.8	8.4	8.0	8.4	8.0	8.0
87.5°	6.2	4.9	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
90°	0.8	2.8	4.8	6.9	8.9	9.9	11.8	15.5	19.2	23.0	26.7
92.5°	16.8	18.2	19.5	20.9	22.2	22.9	23.0	23.2	23.3	23.5	23.7
95°	39.7	41.4	43.1	44.8	46.5	47.3	47.5	47.8	48.2	48.5	48.9
97.5°	66.4	67.9	69.5	71.0	72.5	73.3	73.6	74.3	75.0	75.6	76.3
100°	97.0	98.4	99.7	101.1	102.4	103.1	103.4	103.9	104.4	104.9	105.4
102.5°	129.0	130.0	131.0	132.1	133.1	133.6	133.9	134.6	135.3	136.0	136.7
105°	164.1	164.6	165.1	165.6	166.1	166.4	166.6	166.9	167.3	167.6	168.0
107.5°	199.3	200.0	200.6	201.3	202.0	202.3	202.3	202.3	202.3	202.3	202.3
110°	232.9	233.9	234.9	235.9	236.9	237.4	237.4	237.4	237.4	237.4	237.4

TEST NUMBER: P1009897

CATALOG NUMBER: S122RDIP-B290D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	269.5	270.5	271.5	272.6	273.6	274.1	274.0	273.8	273.7	273.5	273.3
115°	305.4	306.4	307.4	308.5	309.5	310.0	309.8	309.5	309.1	308.8	308.4
117.5°	341.3	342.7	344.0	345.4	346.7	347.4	347.0	346.1	345.3	344.4	343.6
120°	377.2	378.6	379.9	381.3	382.6	383.3	382.6	381.3	379.9	378.6	377.2
122.5°	410.0	411.7	413.4	415.1	416.8	417.6	417.2	416.3	415.5	414.6	413.8
125°	444.3	445.8	447.4	448.9	450.4	451.2	450.9	450.4	449.9	449.4	448.9
127.5°	477.9	479.8	481.6	483.5	485.4	486.3	486.0	485.3	484.6	484.0	483.3
130°	509.2	511.4	513.6	515.9	518.1	519.2	519.0	518.7	518.3	518.0	517.6
132.5°	544.4	546.1	547.8	549.5	551.2	552.0	552.1	552.3	552.4	552.6	552.8
135°	574.9	576.8	578.6	580.5	582.4	583.3	583.5	583.8	584.1	584.5	584.8
137.5°	608.5	610.0	611.6	613.1	614.6	615.4	615.6	615.9	616.2	616.6	616.9
140°	638.3	639.8	641.3	642.8	644.3	645.1	645.5	646.4	647.3	648.1	649.0
142.5°	668.8	670.3	671.9	673.4	674.9	675.7	676.0	676.5	677.0	677.5	678.0
145°	697.8	699.0	700.2	701.4	702.6	703.2	703.7	704.7	705.7	706.7	707.7
147.5°	723.8	725.3	726.8	728.3	729.8	730.6	730.9	731.6	732.3	733.0	733.7
150°	750.5	751.5	752.5	753.6	754.6	755.1	755.4	756.1	756.8	757.4	758.1
152.5°	774.2	775.2	776.2	777.2	778.2	778.7	779.1	780.0	780.9	781.7	782.6
155°	797.8	798.3	798.8	799.3	799.8	800.1	800.4	800.9	801.4	801.9	802.4
157.5°	818.4	818.8	819.1	819.5	819.8	820.0	820.2	820.5	820.8	821.2	821.5
160°	836.8	837.1	837.5	837.8	838.1	838.3	838.4	838.6	838.7	838.9	839.1
162.5°	853.6	853.6	853.6	853.6	853.6	853.6	853.7	853.8	854.0	854.1	854.3
165°	868.1	867.9	867.7	867.6	867.4	867.3	867.3	867.3	867.3	867.3	867.3
167.5°	881.1	880.6	880.1	879.6	879.1	878.8	878.8	878.8	878.8	878.8	878.8
170°	891.0	890.5	890.0	889.5	889.0	888.7	888.6	888.4	888.3	888.1	887.9
172.5°	897.8	897.3	896.8	896.3	895.8	895.6	895.5	895.3	895.2	895.0	894.8
175°	903.2	902.7	902.2	901.7	901.2	900.9	900.7	900.4	900.1	899.7	899.4
177.5°	906.2	905.7	905.2	904.7	904.2	904.0	903.8	903.5	903.1	902.8	902.4
180°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7

TEST NUMBER: P1009897

CATALOG NUMBER: S122RDIP-B290D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5
2.5°	659.1	660.0	661.3	667.5	668.4	670.1	669.3	669.3	669.7	668.8	669.3
5°	687.4	688.7	695.4	702.9	704.6	702.9	705.1	708.2	708.2	708.2	707.3
7.5°	713.9	718.8	726.3	737.4	739.6	741.8	745.8	743.1	744.0	748.0	746.7
10°	739.6	746.7	755.1	764.4	769.2	772.3	774.1	778.1	787.4	776.8	780.7
12.5°	763.9	774.1	782.9	793.1	796.7	800.6	802.0	805.5	805.5	805.1	808.2
15°	779.8	789.1	797.1	803.7	804.6	803.7	802.8	803.3	804.6	799.3	802.4
17.5°	783.4	784.3	786.9	784.3	784.7	775.4	770.1	768.8	756.4	756.8	767.0
20°	766.1	751.1	747.1	732.5	723.7	699.8	698.9	692.3	666.2	674.1	672.4
22.5°	718.8	693.1	659.1	642.3	633.9	608.7	589.2	575.5	566.2	556.9	552.9
25°	656.4	614.9	566.6	533.5	528.6	505.2	469.3	452.5	432.6	426.4	437.0
27.5°	575.9	522.0	467.6	416.7	407.4	386.2	368.0	356.1	333.1	331.8	332.6
30°	466.7	412.3	366.7	333.5	310.5	300.8	288.8	280.0	270.7	274.3	275.1
32.5°	383.5	331.8	289.3	271.6	261.0	254.8	244.6	238.9	234.9	233.6	233.1
35°	304.8	270.3	251.2	234.0	227.8	223.4	215.9	213.2	209.7	210.1	210.1
37.5°	261.0	232.2	218.1	209.2	203.5	201.3	196.4	193.7	191.5	190.6	192.0
40°	225.2	205.2	196.4	188.4	183.6	182.7	180.0	176.9	174.3	174.7	176.1
42.5°	199.1	187.6	176.9	170.7	167.2	165.9	163.7	161.5	161.5	160.1	159.7
45°	178.3	169.0	160.1	154.4	152.2	150.4	147.7	147.3	145.5	146.0	146.4
47.5°	159.7	152.2	145.5	139.8	137.6	137.1	134.5	132.7	132.7	132.3	131.8
50°	142.9	135.4	129.6	126.5	123.4	122.5	122.1	121.6	120.8	120.8	121.2
52.5°	129.2	121.6	117.2	114.6	112.8	111.9	111.9	111.5	111.5	111.5	111.0
55°	114.1	107.9	104.4	103.5	102.6	102.2	101.7	100.9	100.4	101.3	100.4
57.5°	100.0	97.8	94.7	93.8	91.6	91.6	90.2	89.4	88.5	89.4	89.4
60°	88.9	85.8	84.0	81.4	79.6	77.9	75.6	75.2	74.3	73.9	73.4
62.5°	77.4	74.8	70.3	66.4	63.7	61.9	61.0	60.6	60.6	60.2	60.2
65°	64.6	58.4	56.2	54.9	54.4	54.0	53.1	52.6	53.1	52.6	53.1
67.5°	50.4	49.5	48.2	47.3	46.9	46.4	46.4	46.0	46.0	46.0	46.0
70°	43.8	41.6	41.1	40.3	40.3	39.8	39.8	39.8	39.8	39.4	40.3
72.5°	36.3	34.9	34.5	34.1	34.1	34.1	33.6	33.6	33.6	33.2	33.6
75°	29.6	29.2	28.3	28.3	27.9	28.3	27.9	27.9	27.4	27.9	27.9
77.5°	23.9	23.4	23.0	23.0	22.6	22.6	22.6	22.6	22.6	22.6	23.0
80°	18.1	17.7	17.3	17.7	17.3	17.7	17.3	17.3	17.7	17.3	17.3
82.5°	13.3	12.8	12.8	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4
85°	8.0	7.5	7.5	8.0	7.5	8.0	7.5	7.5	7.5	8.0	8.0
87.5°	3.5	4.0	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	4.0
90°	26.4	26.0	25.7	25.4	25.2	25.3	25.5	25.6	25.8	26.0	25.8
92.5°	23.9	24.0	24.2	24.3	24.4	24.4	24.4	24.4	24.4	24.4	24.4
95°	48.9	48.9	48.9	48.9	48.9	48.7	48.4	48.0	47.7	47.3	47.7
97.5°	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3
100°	105.4	105.4	105.4	105.4	105.4	105.3	105.1	105.0	104.8	104.6	104.8
102.5°	136.9	137.0	137.2	137.3	137.4	137.3	137.2	137.0	136.9	136.7	136.9
105°	168.3	168.7	169.0	169.3	169.5	169.5	169.5	169.5	169.5	169.5	169.5
107.5°	202.5	202.7	202.8	203.0	203.1	202.7	201.8	201.0	200.1	199.3	200.1
110°	237.4	237.4	237.4	237.4	237.4	237.2	236.7	236.2	235.7	235.2	235.7

TEST NUMBER: P1009897

CATALOG NUMBER: S122RDIP-B290D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	272.8	272.3	271.8	271.3	271.0	270.8	270.5	270.2	269.8	269.5	269.8
115°	308.2	308.1	307.9	307.8	307.7	307.4	306.9	306.4	305.9	305.4	305.9
117.5°	343.1	342.6	342.1	341.6	341.3	341.0	340.5	340.0	339.5	339.0	339.5
120°	377.2	377.2	377.2	377.2	377.2	376.9	376.4	375.9	375.4	374.9	375.4
122.5°	413.3	412.8	412.3	411.8	411.5	411.3	411.0	410.7	410.3	410.0	410.3
125°	448.4	447.9	447.4	446.9	446.6	446.5	446.4	446.2	446.1	445.9	446.1
127.5°	482.6	481.9	481.2	480.5	480.2	479.9	479.4	478.9	478.4	477.9	478.4
130°	517.3	516.9	516.6	516.3	516.1	515.8	515.1	514.4	513.8	513.1	513.8
132.5°	551.9	551.1	550.2	549.3	548.9	548.6	548.1	547.6	547.1	546.6	547.1
135°	584.6	584.5	584.3	584.2	584.1	583.8	583.3	582.8	582.3	581.8	582.3
137.5°	616.7	616.5	616.4	616.2	616.1	615.8	615.1	614.4	613.8	613.1	613.8
140°	649.0	649.0	649.0	649.0	649.0	648.7	648.0	647.3	646.6	645.9	646.6
142.5°	678.2	678.3	678.5	678.6	678.7	678.4	677.7	677.0	676.4	675.7	676.4
145°	707.9	708.1	708.2	708.4	708.5	708.2	707.5	706.8	706.2	705.5	706.2
147.5°	734.0	734.4	734.7	735.0	735.2	734.9	734.2	733.5	732.9	732.2	732.9
150°	758.6	759.1	759.6	760.1	760.4	760.1	759.6	759.1	758.6	758.1	758.6
152.5°	783.3	783.9	784.6	785.3	785.6	785.3	784.6	783.9	783.3	782.6	783.3
155°	803.2	804.1	804.9	805.8	806.2	805.9	805.4	804.9	804.4	803.9	804.4
157.5°	822.7	823.9	825.0	826.2	826.8	826.4	825.5	824.7	823.8	823.0	823.8
160°	840.1	841.1	842.1	843.1	843.6	843.3	842.6	841.9	841.3	840.6	841.3
162.5°	855.5	856.7	857.9	859.1	859.7	859.3	858.4	857.6	856.7	855.9	856.7
165°	868.5	869.7	870.9	872.1	872.7	872.3	871.4	870.5	869.7	868.8	869.7
167.5°	880.0	881.2	882.3	883.5	884.1	883.7	882.8	882.0	881.1	880.3	881.1
170°	889.1	890.3	891.5	892.7	893.3	892.8	891.8	890.7	889.7	888.7	889.7
172.5°	896.0	897.2	898.3	899.5	900.1	899.6	898.6	897.6	896.6	895.6	896.6
175°	900.6	901.8	902.9	904.1	904.7	904.2	903.2	902.1	901.1	900.1	901.1
177.5°	903.4	904.4	905.5	906.5	907.0	906.5	905.5	904.4	903.4	902.4	903.4
180°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7

TEST NUMBER: P1009897

CATALOG NUMBER: S122RDIP-B290D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5
2.5°	671.0	667.9	667.0	667.9	667.0	667.5	664.4	652.9	656.0	651.1	653.8
5°	709.1	706.4	700.7	699.8	698.9	698.0	693.6	683.4	679.4	672.8	672.4
7.5°	745.3	745.3	740.9	737.8	733.8	730.7	725.0	710.0	703.8	695.8	691.4
10°	781.2	769.7	774.5	771.4	761.7	759.9	749.3	740.5	728.5	720.6	713.5
12.5°	806.8	803.3	798.9	796.2	793.6	787.8	780.7	758.2	752.0	736.1	728.1
15°	805.9	803.7	805.1	805.1	804.2	802.8	797.1	780.7	770.1	754.6	740.9
17.5°	762.6	768.3	774.1	778.1	786.9	790.9	796.2	786.5	779.8	766.6	752.0
20°	687.0	701.1	717.9	721.5	729.4	752.9	763.5	771.9	774.5	770.1	758.2
22.5°	581.7	593.6	634.3	633.4	644.9	672.8	703.8	729.0	748.9	759.9	755.5
25°	455.6	472.4	494.1	510.5	548.1	589.6	628.1	668.4	702.9	733.4	740.9
27.5°	344.6	366.7	384.0	405.6	424.6	473.7	523.3	586.1	626.4	684.3	714.4
30°	278.7	288.8	306.1	316.3	325.6	363.2	419.3	481.3	552.0	618.8	670.6
32.5°	238.0	245.1	257.9	262.3	272.0	297.3	332.6	389.3	462.2	543.2	611.3
35°	213.7	221.2	223.8	227.8	235.8	251.7	276.0	317.2	383.1	462.2	543.6
37.5°	192.9	196.8	204.4	207.0	209.7	221.6	238.0	266.7	310.5	375.5	465.8
40°	178.3	180.5	184.5	186.7	188.4	196.8	211.4	230.9	263.2	312.7	395.9
42.5°	162.8	165.4	168.1	170.7	173.0	179.6	188.4	207.0	228.7	266.3	326.4
45°	147.7	149.5	152.6	154.4	157.5	162.8	170.7	183.6	203.0	226.9	275.6
47.5°	134.0	136.2	137.6	139.8	142.0	147.7	155.3	163.7	179.6	203.0	238.4
50°	121.6	124.3	126.1	126.5	128.3	133.6	139.8	149.1	159.2	177.4	208.3
52.5°	112.8	113.2	114.6	116.3	115.9	119.0	124.7	131.8	142.4	157.0	179.6
55°	102.6	104.0	104.8	105.3	105.3	107.9	111.0	117.7	126.1	138.0	157.0
57.5°	89.8	91.1	93.8	94.7	96.0	97.3	98.6	103.1	110.1	121.6	137.1
60°	76.5	77.4	80.1	81.8	82.7	86.3	88.0	91.6	95.5	104.0	118.5
62.5°	61.5	62.4	63.7	65.5	67.2	72.5	77.0	80.5	83.6	89.4	101.3
65°	53.5	54.0	54.9	55.3	55.7	57.9	61.9	66.8	72.5	77.0	84.0
67.5°	46.4	46.9	47.3	48.2	48.7	49.1	50.9	52.2	57.9	64.1	69.4
70°	39.8	40.7	41.1	41.1	41.6	42.5	43.3	45.1	46.9	50.0	56.6
72.5°	33.6	34.1	34.9	34.9	34.9	35.8	36.7	37.6	38.5	40.3	42.9
75°	27.9	28.8	28.8	28.8	29.2	29.2	30.1	31.0	31.8	33.2	34.1
77.5°	23.0	23.0	23.0	23.0	23.4	23.4	23.9	24.8	25.2	25.7	26.5
80°	17.3	17.7	17.7	17.7	18.1	18.1	18.1	19.0	19.5	19.5	20.3
82.5°	12.8	12.8	12.8	13.3	12.8	13.3	13.3	13.7	13.3	13.7	14.2
85°	8.0	8.0	8.0	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.8
87.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.4	4.0	4.0
90°	25.6	25.5	25.3	25.2	25.4	25.7	26.0	26.4	26.7	23.0	19.2
92.5°	24.4	24.4	24.4	24.4	24.3	24.2	24.0	23.9	23.7	23.5	23.3
95°	48.0	48.4	48.7	48.9	48.9	48.9	48.9	48.9	48.9	48.5	48.2
97.5°	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3	75.6	75.0
100°	105.0	105.1	105.3	105.4	105.4	105.4	105.4	105.4	105.4	104.9	104.4
102.5°	137.0	137.2	137.3	137.4	137.3	137.2	137.0	136.9	136.7	136.0	135.3
105°	169.5	169.5	169.5	169.5	169.3	169.0	168.7	168.3	168.0	167.6	167.3
107.5°	201.0	201.8	202.7	203.1	203.0	202.8	202.7	202.5	202.3	202.3	202.3
110°	236.2	236.7	237.2	237.4	237.4	237.4	237.4	237.4	237.4	237.4	237.4

TEST NUMBER: P1009897

CATALOG NUMBER: S122RDIP-B290D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	270.2	270.5	270.8	271.0	271.3	271.8	272.3	272.8	273.3	273.5	273.7
115°	306.4	306.9	307.4	307.7	307.8	307.9	308.1	308.2	308.4	308.8	309.1
117.5°	340.0	340.5	341.0	341.3	341.6	342.1	342.6	343.1	343.6	344.4	345.3
120°	375.9	376.4	376.9	377.2	377.2	377.2	377.2	377.2	377.2	378.6	379.9
122.5°	410.7	411.0	411.3	411.5	411.8	412.3	412.8	413.3	413.8	414.6	415.5
125°	446.2	446.4	446.5	446.6	446.9	447.4	447.9	448.4	448.9	449.4	449.9
127.5°	478.9	479.4	479.9	480.2	480.5	481.2	481.9	482.6	483.3	484.0	484.6
130°	514.4	515.1	515.8	516.1	516.3	516.6	516.9	517.3	517.6	518.0	518.3
132.5°	547.6	548.1	548.6	548.9	549.3	550.2	551.1	551.9	552.8	552.6	552.4
135°	582.8	583.3	583.8	584.1	584.2	584.3	584.5	584.6	584.8	584.5	584.1
137.5°	614.4	615.1	615.8	616.1	616.2	616.4	616.5	616.7	616.9	616.6	616.2
140°	647.3	648.0	648.7	649.0	649.0	649.0	649.0	649.0	649.0	648.1	647.3
142.5°	677.0	677.7	678.4	678.7	678.6	678.5	678.3	678.2	678.0	677.5	677.0
145°	706.8	707.5	708.2	708.5	708.4	708.2	708.1	707.9	707.7	706.7	705.7
147.5°	733.5	734.2	734.9	735.2	735.0	734.7	734.4	734.0	733.7	733.0	732.3
150°	759.1	759.6	760.1	760.4	760.1	759.6	759.1	758.6	758.1	757.4	756.8
152.5°	783.9	784.6	785.3	785.6	785.3	784.6	783.9	783.3	782.6	781.7	780.9
155°	804.9	805.4	805.9	806.2	805.8	804.9	804.1	803.2	802.4	801.9	801.4
157.5°	824.7	825.5	826.4	826.8	826.2	825.0	823.9	822.7	821.5	821.2	820.8
160°	841.9	842.6	843.3	843.6	843.1	842.1	841.1	840.1	839.1	838.9	838.7
162.5°	857.6	858.4	859.3	859.7	859.1	857.9	856.7	855.5	854.3	854.1	854.0
165°	870.5	871.4	872.3	872.7	872.1	870.9	869.7	868.5	867.3	867.3	867.3
167.5°	882.0	882.8	883.7	884.1	883.5	882.3	881.2	880.0	878.8	878.8	878.8
170°	890.7	891.8	892.8	893.3	892.7	891.5	890.3	889.1	887.9	888.1	888.3
172.5°	897.6	898.6	899.6	900.1	899.5	898.3	897.2	896.0	894.8	895.0	895.2
175°	902.1	903.2	904.2	904.7	904.1	902.9	901.8	900.6	899.4	899.7	900.1
177.5°	904.4	905.5	906.5	907.0	906.5	905.5	904.4	903.4	902.4	902.8	903.1
180°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7

TEST NUMBER: P1009897

CATALOG NUMBER: S122RDIP-B290D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5
2.5°	649.8	647.6	647.6	646.3	646.3	639.2	639.2	641.4	638.7	635.6	631.2
5°	666.6	661.7	660.4	658.6	652.9	644.0	640.5	639.2	633.9	627.2	619.7
7.5°	682.5	674.6	670.6	666.6	659.1	646.7	639.6	634.8	626.8	616.6	606.9
10°	698.0	687.8	677.7	672.8	662.2	646.7	636.5	628.6	617.1	603.4	589.6
12.5°	712.2	690.9	689.2	679.4	664.0	646.3	630.8	619.3	604.7	588.8	572.8
15°	724.6	702.9	692.3	683.4	663.1	641.0	624.6	610.4	591.0	572.8	553.4
17.5°	730.7	707.3	700.2	685.6	664.8	636.1	614.0	596.7	575.5	553.8	531.7
20°	736.9	709.5	698.0	687.8	659.5	626.8	602.0	582.1	558.7	533.0	508.7
22.5°	740.0	709.5	695.8	681.6	654.2	616.6	587.4	564.0	536.6	510.5	481.3
25°	734.7	706.9	690.5	675.9	644.9	604.2	570.6	544.1	514.9	485.2	455.6
27.5°	721.5	700.7	681.6	666.6	632.1	588.3	552.9	522.8	492.8	459.6	429.5
30°	696.7	687.4	672.4	655.5	618.0	574.2	532.1	501.2	468.0	434.8	403.4
32.5°	658.2	666.2	656.4	641.8	601.1	554.7	510.0	478.6	442.3	406.5	377.8
35°	611.3	639.6	634.3	624.1	583.4	533.9	489.2	451.2	414.9	378.6	349.9
37.5°	560.0	602.9	607.3	601.1	563.1	512.7	463.6	426.4	389.3	352.5	323.4
40°	489.7	555.6	569.7	572.4	541.9	487.0	435.7	399.4	362.7	326.9	291.5
42.5°	425.1	508.2	525.9	537.0	514.9	461.8	410.0	369.8	333.5	301.2	265.8
45°	364.5	451.2	479.9	494.1	484.4	433.1	379.5	341.9	308.8	279.1	245.1
47.5°	302.1	389.3	429.5	452.1	452.1	403.9	350.3	313.2	281.3	256.1	226.0
50°	260.5	333.1	374.7	404.3	412.3	374.2	323.8	287.5	257.4	230.0	207.0
52.5°	222.1	287.1	321.6	352.5	375.5	342.4	294.2	261.4	231.8	206.1	188.0
55°	192.0	240.6	272.0	306.1	331.8	310.1	265.4	233.6	207.9	186.7	171.2
57.5°	163.2	205.7	231.3	261.4	288.8	272.5	236.7	209.2	186.7	168.1	154.4
60°	138.9	173.4	193.3	216.7	250.8	239.3	209.7	184.5	166.3	149.5	138.0
62.5°	118.1	145.5	162.3	179.1	210.1	204.8	181.8	162.3	146.9	132.7	123.0
65°	96.9	119.4	132.7	147.3	172.1	174.3	155.7	142.0	127.8	115.5	106.6
67.5°	78.3	96.0	107.9	120.3	140.2	146.4	133.6	122.1	110.1	100.0	92.0
70°	63.3	75.6	84.5	94.2	110.6	118.1	111.5	103.5	93.8	85.4	78.3
72.5°	50.0	57.9	63.3	70.8	84.0	91.6	91.1	84.0	77.0	71.2	65.5
75°	36.7	42.9	47.3	52.2	62.8	69.9	71.7	68.6	61.5	57.1	52.6
77.5°	27.9	31.4	33.6	37.2	44.7	50.9	53.5	52.6	47.8	44.2	41.1
80°	21.2	22.1	23.0	24.3	30.5	36.3	38.0	37.6	34.9	33.6	30.1
82.5°	15.0	15.5	15.9	16.4	18.6	23.4	25.2	26.1	23.9	22.6	19.5
85°	8.8	9.3	9.3	10.2	10.6	11.9	15.0	15.0	14.6	12.8	12.4
87.5°	4.4	4.4	4.0	4.0	4.4	4.9	5.8	6.6	5.8	5.3	4.9
90°	15.5	11.8	9.9	8.9	6.9	4.8	2.8	0.8	2.8	4.8	6.9
92.5°	23.2	23.0	22.9	22.2	20.9	19.5	18.2	16.8	18.2	19.5	20.9
95°	47.8	47.5	47.3	46.5	44.8	43.1	41.4	39.7	41.4	43.1	44.8
97.5°	74.3	73.6	73.3	72.5	71.0	69.5	67.9	66.4	67.9	69.5	71.0
100°	103.9	103.4	103.1	102.4	101.1	99.7	98.4	97.0	98.4	99.7	101.1
102.5°	134.6	133.9	133.6	133.1	132.1	131.0	130.0	129.0	130.0	131.0	132.1
105°	166.9	166.6	166.4	166.1	165.6	165.1	164.6	164.1	164.6	165.1	165.6
107.5°	202.3	202.3	202.3	202.0	201.3	200.6	200.0	199.3	200.0	200.6	201.3
110°	237.4	237.4	237.4	236.9	235.9	234.9	233.9	232.9	233.9	234.9	235.9

TEST NUMBER: P1009897

CATALOG NUMBER: S122RDIP-B290D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	273.8	274.0	274.1	273.6	272.6	271.5	270.5	269.5	270.5	271.5	272.6
115°	309.5	309.8	310.0	309.5	308.5	307.4	306.4	305.4	306.4	307.4	308.5
117.5°	346.1	347.0	347.4	346.7	345.4	344.0	342.7	341.3	342.7	344.0	345.4
120°	381.3	382.6	383.3	382.6	381.3	379.9	378.6	377.2	378.6	379.9	381.3
122.5°	416.3	417.2	417.6	416.8	415.1	413.4	411.7	410.0	411.7	413.4	415.1
125°	450.4	450.9	451.2	450.4	448.9	447.4	445.8	444.3	445.8	447.4	448.9
127.5°	485.3	486.0	486.3	485.4	483.5	481.6	479.8	477.9	479.8	481.6	483.5
130°	518.7	519.0	519.2	518.1	515.9	513.6	511.4	509.2	511.4	513.6	515.9
132.5°	552.3	552.1	552.0	551.2	549.5	547.8	546.1	544.4	546.1	547.8	549.5
135°	583.8	583.5	583.3	582.4	580.5	578.6	576.8	574.9	576.8	578.6	580.5
137.5°	615.9	615.6	615.4	614.6	613.1	611.6	610.0	608.5	610.0	611.6	613.1
140°	646.4	645.5	645.1	644.3	642.8	641.3	639.8	638.3	639.8	641.3	642.8
142.5°	676.5	676.0	675.7	674.9	673.4	671.9	670.3	668.8	670.3	671.9	673.4
145°	704.7	703.7	703.2	702.6	701.4	700.2	699.0	697.8	699.0	700.2	701.4
147.5°	731.6	730.9	730.6	729.8	728.3	726.8	725.3	723.8	725.3	726.8	728.3
150°	756.1	755.4	755.1	754.6	753.6	752.5	751.5	750.5	751.5	752.5	753.6
152.5°	780.0	779.1	778.7	778.2	777.2	776.2	775.2	774.2	775.2	776.2	777.2
155°	800.9	800.4	800.1	799.8	799.3	798.8	798.3	797.8	798.3	798.8	799.3
157.5°	820.5	820.2	820.0	819.8	819.5	819.1	818.8	818.4	818.8	819.1	819.5
160°	838.6	838.4	838.3	838.1	837.8	837.5	837.1	836.8	837.1	837.5	837.8
162.5°	853.8	853.7	853.6	853.6	853.6	853.6	853.6	853.6	853.6	853.6	853.6
165°	867.3	867.3	867.3	867.4	867.6	867.7	867.9	868.1	867.9	867.7	867.6
167.5°	878.8	878.8	878.8	879.1	879.6	880.1	880.6	881.1	880.6	880.1	879.6
170°	888.4	888.6	888.7	889.0	889.5	890.0	890.5	891.0	890.5	890.0	889.5
172.5°	895.3	895.5	895.6	895.8	896.3	896.8	897.3	897.8	897.3	896.8	896.3
175°	900.4	900.7	900.9	901.2	901.7	902.2	902.7	903.2	902.7	902.2	901.7
177.5°	903.5	903.8	904.0	904.2	904.7	905.2	905.7	906.2	905.7	905.2	904.7
180°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7

TEST NUMBER: P1009897

CATALOG NUMBER: S122RDIP-B290D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5
2.5°	629.5	629.9	631.2	627.2	621.0	618.4	610.4	609.1	607.8	607.8	609.1
5°	615.3	613.5	614.0	606.4	597.6	592.3	581.2	583.0	577.3	573.7	574.6
7.5°	599.8	594.9	594.5	584.8	573.7	564.0	552.5	549.8	544.5	538.3	535.7
10°	580.4	576.8	570.2	559.1	545.0	537.0	521.5	512.2	510.9	501.6	498.1
12.5°	560.4	554.3	547.6	532.1	516.2	503.4	491.9	481.7	474.6	466.7	461.4
15°	537.4	529.9	522.4	506.0	487.5	474.6	457.4	442.3	421.6	405.2	395.9
17.5°	512.2	503.8	493.7	475.5	457.4	439.7	407.8	390.1	375.5	365.8	360.1
20°	486.1	476.8	466.7	448.5	417.1	386.2	368.5	354.8	345.9	336.2	329.1
22.5°	458.7	449.0	437.9	409.6	376.4	354.8	341.0	328.2	315.4	310.1	306.5
25°	433.1	424.2	410.0	371.6	345.5	325.6	310.1	301.7	295.0	288.0	281.3
27.5°	406.5	390.1	370.2	337.9	321.6	301.2	290.2	284.0	272.5	267.6	264.5
30°	374.7	356.5	337.5	314.5	295.5	281.3	271.2	261.0	254.3	249.5	244.2
32.5°	342.4	325.1	313.2	289.3	275.1	260.5	250.8	244.6	234.9	231.8	229.6
35°	314.5	299.9	289.3	269.8	256.6	243.3	236.2	226.9	220.7	215.0	211.4
37.5°	287.1	279.1	268.1	251.7	237.5	226.9	217.2	214.1	205.7	202.6	199.1
40°	268.1	256.1	246.8	232.7	220.7	209.2	203.0	196.0	190.2	185.3	184.0
42.5°	245.1	236.2	230.9	215.4	203.0	196.4	188.9	180.9	176.5	172.5	167.6
45°	227.8	219.8	212.3	199.9	188.9	180.5	173.8	168.5	161.0	159.2	151.7
47.5°	209.7	201.7	196.0	183.6	173.4	165.4	160.6	153.5	147.3	143.3	139.8
50°	191.5	184.9	179.6	169.0	160.1	151.7	145.1	138.0	135.4	128.7	126.5
52.5°	174.3	169.9	164.1	153.9	145.1	138.0	130.9	125.2	121.2	117.7	115.0
55°	159.7	152.6	150.0	138.9	131.4	123.9	117.7	114.1	109.3	107.0	104.8
57.5°	143.3	139.3	134.9	126.5	118.1	111.0	106.6	101.3	98.6	96.0	94.2
60°	129.2	123.4	119.9	112.8	105.3	98.6	94.7	90.7	87.1	84.9	81.4
62.5°	112.8	108.4	106.2	98.6	92.4	86.3	82.7	78.7	76.1	72.1	67.7
65°	98.6	95.1	92.4	86.3	80.5	74.8	71.2	66.4	62.8	60.6	60.2
67.5°	86.3	83.6	79.6	73.9	68.1	63.7	59.7	55.7	55.3	54.4	54.4
70°	72.5	69.9	67.7	61.5	56.6	51.8	50.9	49.5	48.2	47.8	46.9
72.5°	60.6	58.4	55.7	50.4	45.6	44.2	43.3	42.5	41.1	40.7	40.3
75°	49.1	46.0	44.2	39.4	38.0	37.2	36.3	34.9	34.1	33.6	32.7
77.5°	37.6	34.5	34.5	31.8	31.0	29.6	28.8	27.9	27.4	26.5	26.5
80°	26.5	26.5	25.7	24.3	23.0	22.6	21.2	20.8	20.3	20.8	19.9
82.5°	19.5	17.7	17.7	16.8	15.9	15.5	14.6	14.6	14.2	14.2	14.2
85°	11.1	11.1	10.6	9.7	9.3	9.3	8.8	8.8	8.4	8.4	8.0
87.5°	4.4	4.0	4.4	4.0	4.0	3.5	3.5	3.5	3.1	3.5	3.1
90°	8.9	9.9	11.8	15.5	19.2	23.0	26.7	26.4	26.0	25.7	25.4
92.5°	22.2	22.9	23.0	23.2	23.3	23.5	23.7	23.9	24.0	24.2	24.3
95°	46.5	47.3	47.5	47.8	48.2	48.5	48.9	48.9	48.9	48.9	48.9
97.5°	72.5	73.3	73.6	74.3	75.0	75.6	76.3	76.3	76.3	76.3	76.3
100°	102.4	103.1	103.4	103.9	104.4	104.9	105.4	105.4	105.4	105.4	105.4
102.5°	133.1	133.6	133.9	134.6	135.3	136.0	136.7	136.9	137.0	137.2	137.3
105°	166.1	166.4	166.6	166.9	167.3	167.6	168.0	168.3	168.7	169.0	169.3
107.5°	202.0	202.3	202.3	202.3	202.3	202.3	202.3	202.5	202.7	202.8	203.0
110°	236.9	237.4	237.4	237.4	237.4	237.4	237.4	237.4	237.4	237.4	237.4

TEST NUMBER: P1009897

CATALOG NUMBER: S122RDIP-B290D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	273.6	274.1	274.0	273.8	273.7	273.5	273.3	272.8	272.3	271.8	271.3
115°	309.5	310.0	309.8	309.5	309.1	308.8	308.4	308.2	308.1	307.9	307.8
117.5°	346.7	347.4	347.0	346.1	345.3	344.4	343.6	343.1	342.6	342.1	341.6
120°	382.6	383.3	382.6	381.3	379.9	378.6	377.2	377.2	377.2	377.2	377.2
122.5°	416.8	417.6	417.2	416.3	415.5	414.6	413.8	413.3	412.8	412.3	411.8
125°	450.4	451.2	450.9	450.4	449.9	449.4	448.9	448.4	447.9	447.4	446.9
127.5°	485.4	486.3	486.0	485.3	484.6	484.0	483.3	482.6	481.9	481.2	480.5
130°	518.1	519.2	519.0	518.7	518.3	518.0	517.6	517.3	516.9	516.6	516.3
132.5°	551.2	552.0	552.1	552.3	552.4	552.6	552.8	551.9	551.1	550.2	549.3
135°	582.4	583.3	583.5	583.8	584.1	584.5	584.8	584.6	584.5	584.3	584.2
137.5°	614.6	615.4	615.6	615.9	616.2	616.6	616.9	616.7	616.5	616.4	616.2
140°	644.3	645.1	645.5	646.4	647.3	648.1	649.0	649.0	649.0	649.0	649.0
142.5°	674.9	675.7	676.0	676.5	677.0	677.5	678.0	678.2	678.3	678.5	678.6
145°	702.6	703.2	703.7	704.7	705.7	706.7	707.7	707.9	708.1	708.2	708.4
147.5°	729.8	730.6	730.9	731.6	732.3	733.0	733.7	734.0	734.4	734.7	735.0
150°	754.6	755.1	755.4	756.1	756.8	757.4	758.1	758.6	759.1	759.6	760.1
152.5°	778.2	778.7	779.1	780.0	780.9	781.7	782.6	783.3	783.9	784.6	785.3
155°	799.8	800.1	800.4	800.9	801.4	801.9	802.4	803.2	804.1	804.9	805.8
157.5°	819.8	820.0	820.2	820.5	820.8	821.2	821.5	822.7	823.9	825.0	826.2
160°	838.1	838.3	838.4	838.6	838.7	838.9	839.1	840.1	841.1	842.1	843.1
162.5°	853.6	853.6	853.7	853.8	854.0	854.1	854.3	855.5	856.7	857.9	859.1
165°	867.4	867.3	867.3	867.3	867.3	867.3	867.3	868.5	869.7	870.9	872.1
167.5°	879.1	878.8	878.8	878.8	878.8	878.8	878.8	880.0	881.2	882.3	883.5
170°	889.0	888.7	888.6	888.4	888.3	888.1	887.9	889.1	890.3	891.5	892.7
172.5°	895.8	895.6	895.5	895.3	895.2	895.0	894.8	896.0	897.2	898.3	899.5
175°	901.2	900.9	900.7	900.4	900.1	899.7	899.4	900.6	901.8	902.9	904.1
177.5°	904.2	904.0	903.8	903.5	903.1	902.8	902.4	903.4	904.4	905.5	906.5
180°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7

TEST NUMBER: P1009897

CATALOG NUMBER: S122RDIP-B290D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5
2.5°	609.1	608.2	605.6	606.4	605.1	605.1	604.2	604.2	604.2	606.4	605.1
5°	575.9	572.8	569.7	568.4	567.1	565.8	565.8	565.3	569.3	568.4	571.9
7.5°	534.8	533.9	527.7	527.7	525.5	524.6	526.8	527.3	527.7	528.6	530.8
10°	498.1	495.9	487.0	487.9	486.6	484.8	486.1	485.2	488.3	489.2	488.3
12.5°	454.7	450.7	441.0	436.1	430.8	426.9	431.7	428.2	440.6	444.1	453.8
15°	397.2	389.7	383.1	383.1	378.2	374.7	376.9	380.9	383.5	387.5	389.3
17.5°	358.7	355.6	350.3	347.2	345.9	344.6	344.6	346.4	352.1	351.7	355.2
20°	326.0	324.2	321.6	317.6	316.3	315.4	315.4	315.4	319.4	322.9	325.1
22.5°	303.4	302.1	300.3	295.0	292.4	291.5	293.7	295.0	298.1	300.8	303.0
25°	280.9	277.8	274.7	272.9	271.6	271.6	272.5	272.9	274.3	275.6	278.2
27.5°	262.3	260.1	255.7	250.8	250.8	249.5	250.4	251.2	254.3	258.8	261.0
30°	241.5	241.1	239.3	237.5	235.8	234.9	236.7	238.0	238.4	240.6	240.6
32.5°	226.5	223.4	220.3	218.5	217.6	217.2	217.6	219.4	219.4	222.1	225.2
35°	211.4	209.7	206.6	203.5	202.6	200.4	202.1	203.9	207.0	208.3	209.7
37.5°	195.1	192.9	191.5	190.6	188.9	189.3	188.0	190.6	193.3	192.9	193.7
40°	182.7	178.7	174.7	174.3	173.8	173.4	173.4	173.8	175.6	177.4	180.0
42.5°	166.8	165.4	161.9	158.4	157.5	156.6	155.7	157.5	161.0	164.1	165.4
45°	150.4	148.6	147.7	145.1	143.3	142.9	142.0	144.2	147.3	148.6	149.5
47.5°	135.4	134.9	132.3	132.7	131.4	131.8	131.4	132.7	132.7	134.0	134.9
50°	125.2	123.9	122.5	121.6	120.3	120.3	119.9	120.3	122.1	123.9	123.4
52.5°	115.0	112.8	112.4	111.9	111.0	111.9	110.6	111.0	112.8	113.7	113.2
55°	103.1	102.6	101.7	100.9	100.4	100.0	100.0	100.0	101.7	103.1	103.5
57.5°	93.8	91.6	89.8	89.8	88.0	87.6	88.5	88.9	90.2	91.1	92.0
60°	80.9	80.1	77.4	76.1	73.4	73.0	73.0	74.8	77.0	80.1	80.9
62.5°	67.2	65.9	65.5	65.5	65.5	65.5	65.5	65.5	65.5	65.9	65.9
65°	59.7	60.2	59.7	59.3	59.7	59.7	59.3	59.3	59.3	59.7	60.2
67.5°	53.5	53.1	53.5	53.1	52.6	52.6	52.2	52.6	53.1	53.5	53.5
70°	46.4	46.4	46.0	46.4	46.0	45.6	45.1	45.1	46.0	46.4	46.4
72.5°	39.8	39.8	39.4	39.4	38.5	38.5	38.9	38.5	38.5	39.8	39.8
75°	33.2	32.7	32.3	32.3	31.8	31.8	31.8	31.4	32.3	32.3	32.7
77.5°	26.1	26.1	26.1	25.7	25.7	25.2	25.2	25.7	25.7	25.7	26.1
80°	19.9	19.9	19.9	19.5	19.0	19.0	19.0	19.0	19.0	19.5	19.0
82.5°	13.7	13.7	13.7	13.7	13.7	13.3	13.3	13.3	13.7	13.7	13.3
85°	8.4	8.0	8.4	8.4	8.0	8.4	8.0	8.0	7.5	7.5	8.0
87.5°	3.5	3.1	2.7	2.7	3.1	2.7	2.7	2.7	3.1	2.7	2.7
90°	25.2	25.3	25.5	25.6	25.8	26.0	25.8	25.6	25.5	25.3	25.2
92.5°	24.4	24.4	24.4	24.4	24.4	24.4	24.4	24.4	24.4	24.4	24.4
95°	48.9	48.7	48.4	48.0	47.7	47.3	47.7	48.0	48.4	48.7	48.9
97.5°	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3
100°	105.4	105.3	105.1	105.0	104.8	104.6	104.8	105.0	105.1	105.3	105.4
102.5°	137.4	137.3	137.2	137.0	136.9	136.7	136.9	137.0	137.2	137.3	137.4
105°	169.5	169.5	169.5	169.5	169.5	169.5	169.5	169.5	169.5	169.5	169.5
107.5°	203.1	202.7	201.8	201.0	200.1	199.3	200.1	201.0	201.8	202.7	203.1
110°	237.4	237.2	236.7	236.2	235.7	235.2	235.7	236.2	236.7	237.2	237.4

TEST NUMBER: P1009897

CATALOG NUMBER: S122RDIP-B290D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	271.0	270.8	270.5	270.2	269.8	269.5	269.8	270.2	270.5	270.8	271.0
115°	307.7	307.4	306.9	306.4	305.9	305.4	305.9	306.4	306.9	307.4	307.7
117.5°	341.3	341.0	340.5	340.0	339.5	339.0	339.5	340.0	340.5	341.0	341.3
120°	377.2	376.9	376.4	375.9	375.4	374.9	375.4	375.9	376.4	376.9	377.2
122.5°	411.5	411.3	411.0	410.7	410.3	410.0	410.3	410.7	411.0	411.3	411.5
125°	446.6	446.5	446.4	446.2	446.1	445.9	446.1	446.2	446.4	446.5	446.6
127.5°	480.2	479.9	479.4	478.9	478.4	477.9	478.4	478.9	479.4	479.9	480.2
130°	516.1	515.8	515.1	514.4	513.8	513.1	513.8	514.4	515.1	515.8	516.1
132.5°	548.9	548.6	548.1	547.6	547.1	546.6	547.1	547.6	548.1	548.6	548.9
135°	584.1	583.8	583.3	582.8	582.3	581.8	582.3	582.8	583.3	583.8	584.1
137.5°	616.1	615.8	615.1	614.4	613.8	613.1	613.8	614.4	615.1	615.8	616.1
140°	649.0	648.7	648.0	647.3	646.6	645.9	646.6	647.3	648.0	648.7	649.0
142.5°	678.7	678.4	677.7	677.0	676.4	675.7	676.4	677.0	677.7	678.4	678.7
145°	708.5	708.2	707.5	706.8	706.2	705.5	706.2	706.8	707.5	708.2	708.5
147.5°	735.2	734.9	734.2	733.5	732.9	732.2	732.9	733.5	734.2	734.9	735.2
150°	760.4	760.1	759.6	759.1	758.6	758.1	758.6	759.1	759.6	760.1	760.4
152.5°	785.6	785.3	784.6	783.9	783.3	782.6	783.3	783.9	784.6	785.3	785.6
155°	806.2	805.9	805.4	804.9	804.4	803.9	804.4	804.9	805.4	805.9	806.2
157.5°	826.8	826.4	825.5	824.7	823.8	823.0	823.8	824.7	825.5	826.4	826.8
160°	843.6	843.3	842.6	841.9	841.3	840.6	841.3	841.9	842.6	843.3	843.6
162.5°	859.7	859.3	858.4	857.6	856.7	855.9	856.7	857.6	858.4	859.3	859.7
165°	872.7	872.3	871.4	870.5	869.7	868.8	869.7	870.5	871.4	872.3	872.7
167.5°	884.1	883.7	882.8	882.0	881.1	880.3	881.1	882.0	882.8	883.7	884.1
170°	893.3	892.8	891.8	890.7	889.7	888.7	889.7	890.7	891.8	892.8	893.3
172.5°	900.1	899.6	898.6	897.6	896.6	895.6	896.6	897.6	898.6	899.6	900.1
175°	904.7	904.2	903.2	902.1	901.1	900.1	901.1	902.1	903.2	904.2	904.7
177.5°	907.0	906.5	905.5	904.4	903.4	902.4	903.4	904.4	905.5	906.5	907.0
180°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7

TEST NUMBER: P1009897

CATALOG NUMBER: S122RDIP-B290D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5
2.5°	606.4	608.7	607.8	602.9	607.8	609.1	611.8	614.4	616.2	618.8	621.0
5°	568.4	572.8	575.5	572.8	581.7	583.0	589.2	592.7	598.0	602.5	606.0
7.5°	532.6	536.1	541.4	542.3	547.6	553.8	562.7	571.5	579.9	584.3	588.3
10°	494.1	500.3	508.2	506.5	514.4	524.2	533.5	547.6	554.7	562.7	569.7
12.5°	455.6	459.6	470.2	473.7	485.2	492.8	505.6	514.4	532.1	541.4	547.6
15°	388.4	404.7	418.0	433.9	449.0	463.1	474.6	490.6	506.0	513.1	523.3
17.5°	357.9	365.4	373.3	381.3	400.8	426.0	446.3	463.6	476.8	486.1	498.1
20°	326.0	333.5	342.4	349.9	361.8	380.0	405.2	434.8	450.7	460.5	472.0
22.5°	303.4	310.5	316.3	322.9	332.2	345.5	364.5	401.2	422.4	434.4	444.6
25°	279.1	288.0	294.2	299.0	306.5	321.1	336.6	357.4	395.5	404.7	418.9
27.5°	262.3	265.0	272.0	279.6	287.1	295.0	311.0	328.7	354.3	374.7	391.9
30°	242.4	249.0	255.7	258.8	265.4	276.9	286.6	305.7	325.6	341.5	362.3
32.5°	227.4	231.3	235.8	243.3	249.5	257.4	267.2	283.1	299.9	310.1	326.0
35°	210.6	213.2	222.5	225.6	231.8	239.7	249.5	261.9	280.0	288.0	299.5
37.5°	194.6	200.8	203.5	210.6	216.3	224.3	231.3	245.5	257.4	266.7	277.3
40°	182.2	184.9	189.8	196.0	200.8	207.0	215.9	226.0	238.9	246.4	255.7
42.5°	167.2	169.4	175.6	179.1	187.1	192.9	198.2	210.6	222.1	227.8	237.1
45°	150.8	156.1	160.1	167.2	171.6	178.7	185.3	194.2	204.8	211.4	216.7
47.5°	136.7	142.0	146.0	152.6	159.7	162.8	169.9	179.1	188.9	194.2	201.7
50°	125.2	127.0	134.5	137.6	145.1	151.3	156.1	164.1	174.7	177.8	184.0
52.5°	114.1	115.5	120.3	124.3	130.9	136.2	142.4	150.0	158.8	163.7	168.5
55°	104.4	105.3	107.5	111.9	116.3	123.0	128.7	135.8	143.3	148.6	153.0
57.5°	93.3	95.1	96.9	99.5	104.0	110.1	116.3	123.0	129.2	132.7	138.5
60°	80.5	83.2	86.3	89.4	92.4	96.9	104.0	110.1	115.9	119.0	123.4
62.5°	66.8	72.1	74.8	78.3	80.9	84.9	90.2	97.3	101.3	105.3	108.8
65°	60.2	60.6	61.0	64.6	69.4	73.4	78.3	83.6	89.8	92.4	95.1
67.5°	53.5	54.0	54.9	55.3	57.1	61.5	66.8	72.5	77.4	79.2	81.8
70°	46.9	46.9	48.7	49.1	49.5	50.0	54.4	60.2	64.6	66.8	69.9
72.5°	39.8	40.3	41.1	41.6	42.5	43.3	44.7	47.8	53.1	55.3	58.8
75°	32.7	33.2	33.6	34.1	35.4	35.8	37.2	38.9	41.1	43.8	46.0
77.5°	26.1	26.1	26.5	27.4	28.3	28.8	30.1	31.0	31.8	33.2	34.9
80°	19.5	19.9	19.9	20.8	20.8	21.2	21.7	23.0	23.9	24.8	25.7
82.5°	13.3	14.2	14.2	14.2	14.6	15.0	15.5	15.5	16.4	16.8	18.1
85°	8.0	8.4	8.4	8.4	8.0	8.8	8.8	9.3	9.3	9.3	9.7
87.5°	3.1	2.7	3.1	3.1	3.1	3.5	3.1	3.1	3.5	4.0	4.0
90°	25.4	25.7	26.0	26.4	26.7	23.0	19.2	15.5	11.8	9.9	8.9
92.5°	24.3	24.2	24.0	23.9	23.7	23.5	23.3	23.2	23.0	22.9	22.2
95°	48.9	48.9	48.9	48.9	48.9	48.5	48.2	47.8	47.5	47.3	46.5
97.5°	76.3	76.3	76.3	76.3	76.3	75.6	75.0	74.3	73.6	73.3	72.5
100°	105.4	105.4	105.4	105.4	105.4	104.9	104.4	103.9	103.4	103.1	102.4
102.5°	137.3	137.2	137.0	136.9	136.7	136.0	135.3	134.6	133.9	133.6	133.1
105°	169.3	169.0	168.7	168.3	168.0	167.6	167.3	166.9	166.6	166.4	166.1
107.5°	203.0	202.8	202.7	202.5	202.3	202.3	202.3	202.3	202.3	202.3	202.0
110°	237.4	237.4	237.4	237.4	237.4	237.4	237.4	237.4	237.4	237.4	236.9

TEST NUMBER: P1009897

CATALOG NUMBER: S122RDIP-B290D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	271.3	271.8	272.3	272.8	273.3	273.5	273.7	273.8	274.0	274.1	273.6
115°	307.8	307.9	308.1	308.2	308.4	308.8	309.1	309.5	309.8	310.0	309.5
117.5°	341.6	342.1	342.6	343.1	343.6	344.4	345.3	346.1	347.0	347.4	346.7
120°	377.2	377.2	377.2	377.2	377.2	378.6	379.9	381.3	382.6	383.3	382.6
122.5°	411.8	412.3	412.8	413.3	413.8	414.6	415.5	416.3	417.2	417.6	416.8
125°	446.9	447.4	447.9	448.4	448.9	449.4	449.9	450.4	450.9	451.2	450.4
127.5°	480.5	481.2	481.9	482.6	483.3	484.0	484.6	485.3	486.0	486.3	485.4
130°	516.3	516.6	516.9	517.3	517.6	518.0	518.3	518.7	519.0	519.2	518.1
132.5°	549.3	550.2	551.1	551.9	552.8	552.6	552.4	552.3	552.1	552.0	551.2
135°	584.2	584.3	584.5	584.6	584.8	584.5	584.1	583.8	583.5	583.3	582.4
137.5°	616.2	616.4	616.5	616.7	616.9	616.6	616.2	615.9	615.6	615.4	614.6
140°	649.0	649.0	649.0	649.0	649.0	648.1	647.3	646.4	645.5	645.1	644.3
142.5°	678.6	678.5	678.3	678.2	678.0	677.5	677.0	676.5	676.0	675.7	674.9
145°	708.4	708.2	708.1	707.9	707.7	706.7	705.7	704.7	703.7	703.2	702.6
147.5°	735.0	734.7	734.4	734.0	733.7	733.0	732.3	731.6	730.9	730.6	729.8
150°	760.1	759.6	759.1	758.6	758.1	757.4	756.8	756.1	755.4	755.1	754.6
152.5°	785.3	784.6	783.9	783.3	782.6	781.7	780.9	780.0	779.1	778.7	778.2
155°	805.8	804.9	804.1	803.2	802.4	801.9	801.4	800.9	800.4	800.1	799.8
157.5°	826.2	825.0	823.9	822.7	821.5	821.2	820.8	820.5	820.2	820.0	819.8
160°	843.1	842.1	841.1	840.1	839.1	838.9	838.7	838.6	838.4	838.3	838.1
162.5°	859.1	857.9	856.7	855.5	854.3	854.1	854.0	853.8	853.7	853.6	853.6
165°	872.1	870.9	869.7	868.5	867.3	867.3	867.3	867.3	867.3	867.3	867.4
167.5°	883.5	882.3	881.2	880.0	878.8	878.8	878.8	878.8	878.8	878.8	879.1
170°	892.7	891.5	890.3	889.1	887.9	888.1	888.3	888.4	888.6	888.7	889.0
172.5°	899.5	898.3	897.2	896.0	894.8	895.0	895.2	895.3	895.5	895.6	895.8
175°	904.1	902.9	901.8	900.6	899.4	899.7	900.1	900.4	900.7	900.9	901.2
177.5°	906.5	905.5	904.4	903.4	902.4	902.8	903.1	903.5	903.8	904.0	904.2
180°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7

TEST NUMBER: P1009897

CATALOG NUMBER: S122RDIP-B290D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	636.5	636.5	636.5	636.5
2.5°	625.0	623.7	631.7	640.5
5°	612.2	614.4	624.6	637.0
7.5°	598.9	603.8	615.7	632.1
10°	580.4	589.2	607.3	624.1
12.5°	562.2	574.2	591.4	611.3
15°	541.9	555.1	576.4	600.3
17.5°	519.3	534.3	559.1	585.2
20°	495.4	515.3	541.4	569.7
22.5°	468.9	492.8	519.8	551.2
25°	443.2	469.3	496.3	532.6
27.5°	418.0	443.7	473.7	510.5
30°	392.8	416.2	448.5	487.9
32.5°	365.8	390.1	424.2	464.5
35°	341.0	365.4	397.2	437.0
37.5°	314.5	340.6	371.1	412.3
40°	283.5	314.1	343.7	383.1
42.5°	257.9	290.2	318.9	356.1
45°	237.5	268.1	291.9	328.2
47.5°	218.5	243.3	267.6	301.2
50°	200.4	219.4	244.6	274.7
52.5°	181.8	198.2	219.8	248.2
55°	165.0	180.5	199.9	221.6
57.5°	149.5	160.6	180.0	199.5
60°	132.3	143.8	158.8	175.2
62.5°	117.7	126.5	140.7	154.4
65°	102.2	110.6	121.2	134.0
67.5°	88.0	95.5	104.0	114.1
70°	75.2	80.9	87.1	96.0
72.5°	61.5	67.7	73.4	80.5
75°	50.4	53.1	57.9	62.8
77.5°	38.9	42.5	45.1	49.1
80°	27.9	31.0	31.8	34.9
82.5°	18.6	20.3	22.1	23.0
85°	10.6	11.5	13.3	13.7
87.5°	4.0	4.4	5.3	6.2
90°	6.9	4.8	2.8	0.8
92.5°	20.9	19.5	18.2	16.8
95°	44.8	43.1	41.4	39.7
97.5°	71.0	69.5	67.9	66.4
100°	101.1	99.7	98.4	97.0
102.5°	132.1	131.0	130.0	129.0
105°	165.6	165.1	164.6	164.1
107.5°	201.3	200.6	200.0	199.3
110°	235.9	234.9	233.9	232.9

TEST NUMBER: P1009897

CATALOG NUMBER: S122RDIP-B290D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	272.6	271.5	270.5	269.5
115°	308.5	307.4	306.4	305.4
117.5°	345.4	344.0	342.7	341.3
120°	381.3	379.9	378.6	377.2
122.5°	415.1	413.4	411.7	410.0
125°	448.9	447.4	445.8	444.3
127.5°	483.5	481.6	479.8	477.9
130°	515.9	513.6	511.4	509.2
132.5°	549.5	547.8	546.1	544.4
135°	580.5	578.6	576.8	574.9
137.5°	613.1	611.6	610.0	608.5
140°	642.8	641.3	639.8	638.3
142.5°	673.4	671.9	670.3	668.8
145°	701.4	700.2	699.0	697.8
147.5°	728.3	726.8	725.3	723.8
150°	753.6	752.5	751.5	750.5
152.5°	777.2	776.2	775.2	774.2
155°	799.3	798.8	798.3	797.8
157.5°	819.5	819.1	818.8	818.4
160°	837.8	837.5	837.1	836.8
162.5°	853.6	853.6	853.6	853.6
165°	867.6	867.7	867.9	868.1
167.5°	879.6	880.1	880.6	881.1
170°	889.5	890.0	890.5	891.0
172.5°	896.3	896.8	897.3	897.8
175°	901.7	902.2	902.7	903.2
177.5°	904.7	905.2	905.7	906.2
180°	904.7	904.7	904.7	904.7

(END OF REPORT)