

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009916

Luminaire Tested: S122RDIP-B290D725UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009916
REPORT IS A COMBINATION OF REPORTS P988174 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B290D725UB50-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3718.0 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009916

CATALOG NUMBER: S122RDIP-B290D725UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1009916

CATALOG NUMBER: S122RDIP-B290D725UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	86	83	84	80	77	75	63	61	59	47	46	45	33	32	31
2	85	79	73	68	76	71	66	62	56	53	50	42	40	38	29	28	27
3	78	69	63	57	70	63	57	52	50	46	42	38	35	33	26	25	24
4	72	62	54	49	64	56	49	45	44	40	36	34	31	29	24	22	21
5	66	55	48	42	59	50	43	38	40	35	32	31	27	25	22	20	18
6	61	49	42	36	54	45	38	34	36	31	28	28	25	22	20	18	17
7	56	45	37	32	50	41	34	30	33	28	25	25	22	20	18	16	15
8	52	41	33	28	47	37	31	26	30	25	22	23	20	18	17	15	13
9	49	37	30	25	44	34	28	23	27	23	20	21	18	16	16	14	12
10	45	34	27	23	41	31	25	21	25	21	18	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9681	9681	9681	9681
5°	9705	10284	9738	8215
10°	9597	10870	9666	6785
15°	9390	10874	9549	5096
20°	9140	8988	9338	4205
25°	8836	5615	9026	3577
30°	8447	3595	8677	3080
35°	7975	2763	8235	2635
40°	7450	2323	7768	2305
45°	6888	1978	7177	1935
50°	6313	1679	6607	1674
55°	5673	1459	5979	1441
60°	5107	1113	5377	1099
65°	4579	838	4849	951
70°	3993	669	4309	775
75°	3379	513	3686	586
80°	2683	349	2882	385
85°	1865	181	2048	190

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 8856 cd/sqm

TEST NUMBER: P1009916

CATALOG NUMBER: S122RDIP-B290D725UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.0	1.6
10°-20°	161.9	4.4
20°-30°	208.4	5.6
30°-40°	197.7	5.3
40°-50°	169.5	4.6
50°-60°	129.0	3.5
60°-70°	81.4	2.2
70°-80°	40.6	1.1
80°-90°	12.9	0.3
90°-100°	148.8	4.0
100°-110°	524.1	14.1
110°-120°	550.4	14.8
120°-130°	452.8	12.2
130°-140°	363.8	9.8
140°-150°	274.8	7.4
150°-160°	193.2	5.2
160°-170°	113.7	3.1
170°-180°	37.0	1.0
0°-30°	428.4	11.5
0°-40°	626.1	16.8
0°-60°	924.6	24.9
0°-90°	1059.5	28.5
90°-120°	1223.3	32.9
90°-150°	2314.7	62.3
90°-180°	2659.0	71.5
0°-180°	3718.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	612	612	612	612	612	
5°	612	680	614	544	612	58
15°	577	768	587	360	577	162
25°	512	410	523	261	512	235
35°	420	202	434	192	420	263
45°	315	140	329	137	315	243
55°	213	97	224	96	213	192
65°	129	51	136	57	129	128
75°	60	27	66	31	60	65
85°	13	8	14	8	13	15
90°	1	24	1	24	1	3
95°	26	84	26	84	26	27
105°	90	827	90	827	90	95
115°	158	1089	158	1089	158	157
125°	220	883	220	883	220	196
135°	258	732	258	732	258	200
145°	295	584	295	584	295	185
155°	336	491	336	491	336	154
165°	366	431	366	431	366	103
175°	381	388	381	388	381	36
180°	382	382	382	382	382	

TEST NUMBER: P1009916

CATALOG NUMBER: S122RDIP-B290D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6
2.5°	615.5	618.0	619.3	621.0	624.8	627.4	631.2	632.0	631.6	633.3	628.6
5°	612.1	617.6	622.7	626.9	633.7	638.0	642.7	648.2	649.5	655.9	652.0
7.5°	607.4	615.5	622.7	631.2	641.4	646.9	654.2	662.7	666.5	674.1	676.3
10°	599.7	611.2	623.5	632.5	646.5	656.3	663.1	676.7	685.6	697.1	695.4
12.5°	587.4	602.3	618.9	633.7	652.0	658.4	671.2	685.2	696.7	707.3	716.6
15°	576.8	593.8	612.1	630.3	651.2	663.1	675.8	694.1	706.4	725.1	733.2
17.5°	562.3	584.0	605.7	626.1	650.8	664.4	680.1	697.9	716.2	734.1	740.4
20°	547.5	570.8	594.2	621.8	649.9	663.1	679.2	701.3	719.2	733.2	733.2
22.5°	529.6	558.1	584.9	611.2	641.8	661.0	677.5	703.5	716.2	719.2	707.7
25°	511.8	540.2	569.6	602.3	637.1	654.2	672.9	697.1	701.3	689.4	659.7
27.5°	490.5	522.4	555.5	590.8	627.4	648.6	665.6	681.8	673.7	641.8	595.5
30°	468.8	503.3	540.7	574.2	618.4	638.0	652.5	657.1	631.6	579.8	519.8
32.5°	446.3	479.9	519.4	559.8	604.4	623.1	632.5	620.1	573.4	507.9	434.8
35°	419.9	457.8	499.0	541.1	585.3	599.3	604.8	574.7	514.7	430.1	357.5
37.5°	396.1	434.0	478.2	521.1	564.0	571.7	566.2	519.0	442.9	359.2	288.2
40°	368.1	408.5	451.8	499.9	535.1	537.3	523.7	462.5	368.1	289.5	245.7
42.5°	342.2	383.0	426.3	475.2	502.0	494.8	476.5	396.1	307.3	249.5	214.2
45°	315.4	354.1	400.8	444.2	463.3	446.3	418.7	333.2	258.0	214.6	187.4
47.5°	289.5	325.6	371.9	413.6	417.0	397.8	365.1	279.3	223.6	188.7	166.6
50°	264.0	300.1	343.4	377.9	374.5	348.1	311.1	242.7	194.2	166.6	148.3
52.5°	238.5	271.2	313.3	340.5	326.0	300.5	264.0	205.7	169.6	145.4	131.3
55°	212.9	243.6	279.7	302.2	279.3	249.9	224.0	176.4	147.1	127.5	116.9
57.5°	191.7	215.9	249.1	262.7	235.1	212.1	189.6	151.7	127.5	113.5	101.2
60°	168.3	190.4	217.6	225.7	197.2	178.5	159.4	128.4	109.2	96.9	88.8
62.5°	148.3	166.6	187.4	187.4	162.4	148.3	133.9	107.5	91.8	82.0	78.2
65°	128.8	142.0	156.8	155.1	133.9	121.6	110.1	88.8	76.9	70.1	66.3
67.5°	109.7	119.9	129.6	123.7	108.4	97.8	87.1	71.8	63.8	59.1	54.0
70°	92.2	100.3	105.4	99.9	84.6	75.7	68.0	57.8	51.4	45.5	42.5
72.5°	77.4	80.8	82.5	75.7	62.9	57.8	52.3	45.1	39.5	36.6	35.7
75°	60.4	63.3	62.1	57.0	46.3	42.5	38.3	33.2	31.9	30.2	29.3
77.5°	47.2	47.2	45.1	40.4	33.2	30.2	28.5	25.9	24.7	24.2	23.4
80°	33.6	33.2	31.9	26.8	22.5	20.8	20.8	19.1	18.7	17.9	17.9
82.5°	22.1	22.1	20.4	16.2	14.9	14.5	14.0	13.2	13.2	12.8	12.8
85°	13.2	12.3	10.2	8.9	8.5	8.5	8.1	7.7	8.1	7.7	7.7
87.5°	6.0	4.7	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
90°	0.7	2.9	5.9	7.3	8.8	9.9	11.0	14.7	19.8	24.2	25.0
92.5°	11.0	15.4	21.3	25.0	30.8	34.8	38.9	58.7	86.6	111.6	113.1
95°	25.7	28.6	36.0	42.6	54.3	63.1	71.9	105.7	169.6	254.7	287.8
97.5°	38.2	42.6	50.7	60.2	73.4	83.3	93.2	136.6	225.4	362.7	469.1
100°	56.5	58.7	65.3	77.1	91.8	102.0	112.3	151.2	240.8	399.4	580.0
102.5°	73.4	74.9	81.5	93.2	108.7	119.0	129.2	164.4	241.5	385.4	583.6
105°	89.6	92.5	97.6	108.7	124.8	135.1	145.4	179.9	245.2	366.3	544.0
107.5°	107.2	109.4	114.5	124.8	141.0	151.2	161.5	195.3	253.3	356.1	507.3
110°	124.8	127.7	132.1	141.7	157.1	167.8	178.4	210.7	263.6	353.1	482.3

TEST NUMBER: P1009916

CATALOG NUMBER: S122RDIP-B290D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	141.0	143.9	149.0	157.8	172.5	183.5	194.5	225.4	274.6	353.9	466.2
115°	157.8	161.5	165.9	174.7	189.4	199.3	209.2	240.8	285.6	356.8	455.2
117.5°	175.5	178.4	182.8	190.9	204.8	215.1	225.4	254.7	297.3	361.2	449.3
120°	191.6	194.5	199.0	205.6	220.2	230.5	240.8	269.4	309.1	365.6	444.2
122.5°	207.0	209.2	213.6	221.0	235.7	246.3	256.9	283.4	319.4	370.7	441.2
125°	220.2	222.4	226.9	235.7	250.3	260.6	270.9	297.3	330.4	375.9	437.5
127.5°	231.3	234.2	240.1	249.6	263.6	274.2	284.8	310.5	340.6	381.0	435.3
130°	240.8	243.7	251.1	261.4	276.0	286.3	296.6	322.3	350.2	386.9	433.9
132.5°	249.6	253.3	261.4	272.4	287.8	298.0	308.3	332.6	359.7	392.8	433.1
135°	258.4	261.4	270.2	281.2	298.1	308.4	318.6	342.1	367.8	397.2	432.4
137.5°	266.5	270.2	279.0	290.7	307.6	317.2	326.7	350.2	374.4	401.6	432.4
140°	276.0	279.0	287.8	299.5	315.7	325.2	334.8	356.8	379.6	404.5	431.7
142.5°	285.6	287.8	295.9	307.6	323.0	331.8	340.6	361.9	384.0	406.7	431.7
145°	295.1	298.1	305.4	316.4	331.1	339.2	347.2	367.1	387.6	408.2	430.2
147.5°	305.4	307.6	314.9	325.2	337.7	345.0	352.4	371.5	389.8	408.9	428.0
150°	315.7	317.9	323.8	333.3	344.3	350.9	357.5	374.4	391.3	408.2	425.8
152.5°	326.0	326.7	332.6	340.6	350.9	356.8	362.7	377.3	392.0	406.7	422.1
155°	335.5	336.2	340.6	348.7	356.8	362.3	367.8	380.3	392.8	405.2	417.7
157.5°	343.6	344.3	348.0	355.3	361.9	366.7	371.5	382.5	392.8	402.3	413.3
160°	351.7	352.4	355.3	361.2	367.1	371.1	375.1	384.0	392.8	400.1	408.9
162.5°	359.7	359.0	361.9	366.3	371.5	374.4	377.3	384.7	392.0	397.9	405.2
165°	365.6	364.9	366.3	370.7	374.4	376.6	378.8	385.4	390.6	395.0	400.1
167.5°	370.7	370.0	371.5	374.4	377.3	378.8	380.3	385.4	389.8	392.0	395.7
170°	375.9	374.4	375.1	377.3	378.8	379.9	381.0	384.7	388.4	389.8	392.0
172.5°	378.8	378.1	377.3	379.6	380.3	381.0	381.8	384.0	386.2	386.9	387.6
175°	381.0	380.3	379.6	381.0	381.0	381.4	381.8	383.2	384.7	384.0	384.7
177.5°	382.5	381.0	380.3	381.8	381.8	381.8	381.8	382.5	384.0	382.5	381.8
180°	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8

TEST NUMBER: P1009916

CATALOG NUMBER: S122RDIP-B290D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6
2.5°	633.3	634.2	635.4	641.4	642.2	643.9	643.1	643.1	643.5	642.7	643.1
5°	660.5	661.8	668.2	675.4	677.1	675.4	677.5	680.5	680.5	680.5	679.7
7.5°	686.0	690.7	697.9	708.6	710.7	712.8	716.6	714.1	714.9	718.8	717.5
10°	710.7	717.5	725.6	734.5	739.2	742.1	743.8	747.7	756.6	746.4	750.2
12.5°	734.1	743.8	752.3	762.1	765.5	769.3	770.6	774.0	774.0	773.6	776.6
15°	749.4	758.3	765.9	772.3	773.2	772.3	771.5	771.9	773.2	768.1	771.0
17.5°	752.8	753.6	756.2	753.6	754.0	745.1	740.0	738.7	726.8	727.3	737.0
20°	736.2	721.7	717.9	703.9	695.4	672.4	671.6	665.2	640.1	647.8	646.1
22.5°	690.7	666.1	633.3	617.2	609.1	584.9	566.2	553.0	544.1	535.1	531.3
25°	630.8	590.8	544.5	512.6	507.9	485.4	451.0	434.8	415.7	409.7	419.9
27.5°	553.4	501.6	449.3	400.4	391.5	371.1	353.6	342.2	320.1	318.8	319.6
30°	448.4	396.1	352.4	320.5	298.4	289.0	277.6	269.1	260.1	263.5	264.4
32.5°	368.5	318.8	278.0	261.0	250.8	244.8	235.1	229.5	225.7	224.4	224.0
35°	292.9	259.7	241.4	224.9	218.9	214.6	207.4	204.9	201.5	201.9	201.9
37.5°	250.8	223.2	209.5	201.0	195.5	193.4	188.7	186.2	184.0	183.2	184.5
40°	216.4	197.2	188.7	181.1	176.4	175.5	173.0	170.0	167.5	167.9	169.2
42.5°	191.3	180.2	170.0	164.1	160.7	159.4	157.3	155.1	155.1	153.9	153.4
45°	171.3	162.4	153.9	148.3	146.2	144.5	142.0	141.5	139.8	140.3	140.7
47.5°	153.4	146.2	139.8	134.3	132.2	131.8	129.2	127.5	127.5	127.1	126.7
50°	137.3	130.1	124.5	121.6	118.6	117.7	117.3	116.9	116.0	116.0	116.5
52.5°	124.1	116.9	112.6	110.1	108.4	107.5	107.5	107.1	107.1	107.1	106.7
55°	109.7	103.7	100.3	99.5	98.6	98.2	97.8	96.9	96.5	97.3	96.5
57.5°	96.1	93.9	91.0	90.1	88.0	88.0	86.7	85.9	85.0	85.9	85.9
60°	85.4	82.5	80.8	78.2	76.5	74.8	72.7	72.3	71.4	71.0	70.6
62.5°	74.4	71.8	67.6	63.8	61.2	59.5	58.7	58.2	58.2	57.8	57.8
65°	62.1	56.1	54.0	52.7	52.3	51.9	51.0	50.6	51.0	50.6	51.0
67.5°	48.5	47.6	46.3	45.5	45.1	44.6	44.6	44.2	44.2	44.2	44.2
70°	42.1	40.0	39.5	38.7	38.7	38.3	38.3	38.3	38.3	37.8	38.7
72.5°	34.9	33.6	33.2	32.7	32.7	32.7	32.3	32.3	32.3	31.9	32.3
75°	28.5	28.1	27.2	27.2	26.8	27.2	26.8	26.8	26.4	26.8	26.8
77.5°	23.0	22.5	22.1	22.1	21.7	21.7	21.7	21.7	21.7	21.7	22.1
80°	17.4	17.0	16.6	17.0	16.6	17.0	16.6	16.6	17.0	16.6	16.6
82.5°	12.8	12.3	12.3	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9
85°	7.7	7.2	7.2	7.7	7.2	7.7	7.2	7.2	7.2	7.7	7.7
87.5°	3.4	3.8	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.8
90°	24.2	23.5	22.0	23.5	23.8	24.2	24.2	24.2	24.2	24.2	24.2
92.5°	94.7	74.1	63.1	55.1	52.2	49.2	48.5	45.5	46.3	44.8	46.3
95°	251.8	192.3	147.6	116.7	108.6	100.6	91.0	85.2	83.0	83.7	83.0
97.5°	472.8	393.5	314.2	240.1	218.0	196.0	167.4	152.7	144.6	140.2	144.6
100°	685.7	670.3	579.2	478.7	434.2	389.8	328.9	297.3	276.0	262.8	276.0
102.5°	765.0	851.6	848.7	781.9	734.2	686.4	618.9	559.4	531.5	512.4	531.5
105°	739.3	892.0	974.9	984.5	972.4	960.3	914.7	869.2	837.7	827.4	837.7
107.5°	685.0	848.7	972.0	1044.0	1058.6	1073.3	1072.6	1066.0	1056.4	1039.5	1056.4
110°	634.3	789.2	920.6	1014.6	1044.7	1074.8	1106.4	1120.3	1126.9	1126.2	1126.9

TEST NUMBER: P1009916

CATALOG NUMBER: S122RDIP-B290D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	599.1	734.9	859.7	961.7	997.3	1032.9	1079.9	1105.6	1119.6	1124.7	1119.6
115°	571.2	692.3	805.4	901.5	939.3	977.1	1029.3	1063.0	1082.1	1088.7	1082.1
117.5°	552.1	657.1	758.4	847.9	883.9	919.9	973.5	1009.4	1029.3	1034.4	1029.3
120°	537.4	632.1	723.1	800.9	834.4	867.8	919.1	953.7	974.9	982.3	974.9
122.5°	524.9	612.3	693.8	766.4	795.8	825.2	870.0	903.7	922.1	928.0	922.1
125°	513.2	593.2	668.8	733.4	761.0	788.5	831.0	858.9	877.3	883.2	877.3
127.5°	502.2	574.1	643.8	705.5	731.2	756.9	794.3	820.8	836.9	841.3	836.9
130°	491.1	555.7	618.9	676.9	701.1	725.3	761.3	786.3	800.9	806.8	800.9
132.5°	482.3	538.1	595.4	647.5	669.9	692.3	727.5	752.5	765.7	770.8	765.7
135°	474.3	522.0	570.4	618.9	639.4	660.0	691.6	715.8	729.0	731.9	729.0
137.5°	468.4	508.8	550.6	590.3	608.6	627.0	657.1	678.3	690.1	694.5	690.1
140°	463.2	496.3	531.5	565.3	581.4	597.6	621.1	640.2	651.2	655.6	651.2
142.5°	458.1	486.0	514.6	542.5	555.4	568.2	590.3	607.1	616.7	616.7	616.7
145°	453.7	476.5	500.7	523.4	534.0	544.7	562.4	574.8	582.2	584.4	582.2
147.5°	449.3	469.1	488.9	507.3	515.4	523.4	538.9	549.1	554.3	555.7	554.3
150°	443.4	461.0	477.2	492.6	499.2	505.8	516.8	525.6	530.1	530.8	530.1
152.5°	438.3	453.0	467.6	480.1	485.6	491.1	499.2	506.6	509.5	509.5	509.5
155°	431.7	445.6	457.4	468.4	472.4	476.5	484.5	489.7	492.6	491.1	492.6
157.5°	425.8	436.8	447.1	456.6	459.9	463.2	469.1	473.5	475.0	475.0	475.0
160°	419.2	428.7	436.8	444.9	447.4	450.0	455.2	458.8	459.6	459.6	459.6
162.5°	413.3	420.7	427.3	433.9	435.7	437.5	442.7	444.9	445.6	444.9	445.6
165°	406.7	412.6	417.7	422.9	424.4	425.8	428.7	431.7	431.7	430.9	431.7
167.5°	400.1	404.5	408.9	412.6	414.0	415.5	417.0	418.5	418.5	417.7	418.5
170°	395.0	398.6	400.8	403.8	404.5	405.2	406.0	408.2	407.4	406.0	407.4
172.5°	389.8	392.0	393.5	395.7	396.0	396.4	397.2	397.9	397.2	396.4	397.2
175°	385.4	387.6	388.4	389.1	389.5	389.8	389.8	390.6	389.8	388.4	389.8
177.5°	382.5	384.0	384.0	384.7	384.7	384.7	384.7	384.7	384.0	382.5	384.0
180°	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8

TEST NUMBER: P1009916

CATALOG NUMBER: S122RDIP-B290D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6
2.5°	644.8	641.8	641.0	641.8	641.0	641.4	638.4	627.4	630.3	625.7	628.2
5°	681.4	678.8	673.3	672.4	671.6	670.7	666.5	656.7	652.9	646.5	646.1
7.5°	716.2	716.2	712.0	709.0	705.2	702.2	696.7	682.2	676.3	668.6	664.4
10°	750.6	739.6	744.3	741.3	731.9	730.2	720.0	711.5	700.1	692.4	685.6
12.5°	775.3	771.9	767.6	765.1	762.5	757.0	750.2	728.5	722.6	707.3	699.6
15°	774.4	772.3	773.6	773.6	772.7	771.5	765.9	750.2	740.0	725.1	712.0
17.5°	732.8	738.3	743.8	747.7	756.2	760.0	765.1	755.7	749.4	736.6	722.6
20°	660.1	673.7	689.9	693.3	700.9	723.4	733.6	741.7	744.3	740.0	728.5
22.5°	558.9	570.4	609.5	608.7	619.7	646.5	676.3	700.5	719.6	730.2	726.0
25°	437.8	454.0	474.8	490.5	526.6	566.6	603.6	642.2	675.4	704.7	712.0
27.5°	331.1	352.4	368.9	389.8	408.0	455.2	502.8	563.2	601.9	657.6	686.5
30°	267.8	277.6	294.1	303.9	312.8	349.0	402.9	462.5	530.5	594.6	644.4
32.5°	228.7	235.5	247.8	252.1	261.4	285.6	319.6	374.0	444.2	522.0	587.4
35°	205.3	212.5	215.1	218.9	226.6	241.9	265.2	304.8	368.1	444.2	522.4
37.5°	185.3	189.1	196.4	198.9	201.5	212.9	228.7	256.3	298.4	360.9	447.6
40°	171.3	173.4	177.2	179.4	181.1	189.1	203.2	221.9	252.9	300.5	380.4
42.5°	156.4	159.0	161.5	164.1	166.2	172.6	181.1	198.9	219.8	255.9	313.7
45°	142.0	143.7	146.6	148.3	151.3	156.4	164.1	176.4	195.1	218.1	264.8
47.5°	128.8	130.9	132.2	134.3	136.4	142.0	149.2	157.3	172.6	195.1	229.1
50°	116.9	119.4	121.1	121.6	123.3	128.4	134.3	143.2	153.0	170.4	200.2
52.5°	108.4	108.8	110.1	111.8	111.4	114.3	119.9	126.7	136.9	150.9	172.6
55°	98.6	99.9	100.7	101.2	101.2	103.7	106.7	113.1	121.1	132.6	150.9
57.5°	86.3	87.6	90.1	91.0	92.2	93.5	94.8	99.0	105.8	116.9	131.8
60°	73.5	74.4	76.9	78.6	79.5	82.9	84.6	88.0	91.8	99.9	113.9
62.5°	59.1	59.9	61.2	62.9	64.6	69.7	74.0	77.4	80.3	85.9	97.3
65°	51.4	51.9	52.7	53.1	53.6	55.7	59.5	64.2	69.7	74.0	80.8
67.5°	44.6	45.1	45.5	46.3	46.8	47.2	48.9	50.2	55.7	61.6	66.7
70°	38.3	39.1	39.5	39.5	40.0	40.8	41.7	43.4	45.1	48.0	54.4
72.5°	32.3	32.7	33.6	33.6	33.6	34.4	35.3	36.1	37.0	38.7	41.2
75°	26.8	27.6	27.6	27.6	28.1	28.1	28.9	29.8	30.6	31.9	32.7
77.5°	22.1	22.1	22.1	22.1	22.5	22.5	23.0	23.8	24.2	24.7	25.5
80°	16.6	17.0	17.0	17.0	17.4	17.4	17.4	18.3	18.7	18.7	19.6
82.5°	12.3	12.3	12.3	12.8	12.3	12.8	12.8	13.2	12.8	13.2	13.6
85°	7.7	7.7	7.7	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.5
87.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	4.3	3.8	3.8
90°	24.2	24.2	24.2	23.8	23.5	22.0	23.5	24.2	25.0	24.2	19.8
92.5°	45.5	48.5	49.2	52.2	55.1	63.1	74.1	94.7	113.1	111.6	86.6
95°	85.2	91.0	100.6	108.6	116.7	147.6	192.3	251.8	287.8	254.7	169.6
97.5°	152.7	167.4	196.0	218.0	240.1	314.2	393.5	472.8	469.1	362.7	225.4
100°	297.3	328.9	389.8	434.2	478.7	579.2	670.3	685.7	580.0	399.4	240.8
102.5°	559.4	618.9	686.4	734.2	781.9	848.7	851.6	765.0	583.6	385.4	241.5
105°	869.2	914.7	960.3	972.4	984.5	974.9	892.0	739.3	544.0	366.3	245.2
107.5°	1066.0	1072.6	1073.3	1058.6	1044.0	972.0	848.7	685.0	507.3	356.1	253.3
110°	1120.3	1106.4	1074.8	1044.7	1014.6	920.6	789.2	634.3	482.3	353.1	263.6

TEST NUMBER: P1009916

CATALOG NUMBER: S122RDIP-B290D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1105.6	1079.9	1032.9	997.3	961.7	859.7	734.9	599.1	466.2	353.9	274.6
115°	1063.0	1029.3	977.1	939.3	901.5	805.4	692.3	571.2	455.2	356.8	285.6
117.5°	1009.4	973.5	919.9	883.9	847.9	758.4	657.1	552.1	449.3	361.2	297.3
120°	953.7	919.1	867.8	834.4	800.9	723.1	632.1	537.4	444.2	365.6	309.1
122.5°	903.7	870.0	825.2	795.8	766.4	693.8	612.3	524.9	441.2	370.7	319.4
125°	858.9	831.0	788.5	761.0	733.4	668.8	593.2	513.2	437.5	375.9	330.4
127.5°	820.8	794.3	756.9	731.2	705.5	643.8	574.1	502.2	435.3	381.0	340.6
130°	786.3	761.3	725.3	701.1	676.9	618.9	555.7	491.1	433.9	386.9	350.2
132.5°	752.5	727.5	692.3	669.9	647.5	595.4	538.1	482.3	433.1	392.8	359.7
135°	715.8	691.6	660.0	639.4	618.9	570.4	522.0	474.3	432.4	397.2	367.8
137.5°	678.3	657.1	627.0	608.6	590.3	550.6	508.8	468.4	432.4	401.6	374.4
140°	640.2	621.1	597.6	581.4	565.3	531.5	496.3	463.2	431.7	404.5	379.6
142.5°	607.1	590.3	568.2	555.4	542.5	514.6	486.0	458.1	431.7	406.7	384.0
145°	574.8	562.4	544.7	534.0	523.4	500.7	476.5	453.7	430.2	408.2	387.6
147.5°	549.1	538.9	523.4	515.4	507.3	488.9	469.1	449.3	428.0	408.9	389.8
150°	525.6	516.8	505.8	499.2	492.6	477.2	461.0	443.4	425.8	408.2	391.3
152.5°	506.6	499.2	491.1	485.6	480.1	467.6	453.0	438.3	422.1	406.7	392.0
155°	489.7	484.5	476.5	472.4	468.4	457.4	445.6	431.7	417.7	405.2	392.8
157.5°	473.5	469.1	463.2	459.9	456.6	447.1	436.8	425.8	413.3	402.3	392.8
160°	458.8	455.2	450.0	447.4	444.9	436.8	428.7	419.2	408.9	400.1	392.8
162.5°	444.9	442.7	437.5	435.7	433.9	427.3	420.7	413.3	405.2	397.9	392.0
165°	431.7	428.7	425.8	424.4	422.9	417.7	412.6	406.7	400.1	395.0	390.6
167.5°	418.5	417.0	415.5	414.0	412.6	408.9	404.5	400.1	395.7	392.0	389.8
170°	408.2	406.0	405.2	404.5	403.8	400.8	398.6	395.0	392.0	389.8	388.4
172.5°	397.9	397.2	396.4	396.0	395.7	393.5	392.0	389.8	387.6	386.9	386.2
175°	390.6	389.8	389.8	389.5	389.1	388.4	387.6	385.4	384.7	384.0	384.7
177.5°	384.7	384.7	384.7	384.7	384.7	384.0	384.0	382.5	381.8	382.5	384.0
180°	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8

TEST NUMBER: P1009916

CATALOG NUMBER: S122RDIP-B290D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6
2.5°	624.4	622.3	622.3	621.0	621.0	614.2	614.2	616.3	613.8	610.8	606.5
5°	640.5	635.9	634.6	632.9	627.4	618.9	615.5	614.2	609.1	602.7	595.5
7.5°	655.9	648.2	644.4	640.5	633.3	621.4	614.6	609.9	602.3	592.5	583.2
10°	670.7	661.0	651.2	646.5	636.3	621.4	611.6	604.0	592.9	579.8	566.6
12.5°	684.3	663.9	662.2	652.9	638.0	621.0	606.1	595.1	581.0	565.7	550.4
15°	696.2	675.4	665.2	656.7	637.1	615.9	600.2	586.6	567.9	550.4	531.7
17.5°	702.2	679.7	672.9	658.8	638.8	611.2	590.0	573.4	553.0	532.2	510.9
20°	708.1	681.8	670.7	661.0	633.7	602.3	578.5	559.4	536.8	512.2	488.8
22.5°	711.1	681.8	668.6	655.0	628.6	592.5	564.5	541.9	515.6	490.5	462.5
25°	706.0	679.2	663.5	649.5	619.7	580.6	548.3	522.8	494.8	466.3	437.8
27.5°	693.3	673.3	655.0	640.5	607.4	565.3	531.3	502.4	473.5	441.6	412.7
30°	669.5	660.5	646.1	629.9	593.8	551.7	511.3	481.6	449.7	417.8	387.6
32.5°	632.5	640.1	630.8	616.7	577.6	533.0	490.1	459.9	425.0	390.6	363.0
35°	587.4	614.6	609.5	599.7	560.6	513.0	470.1	433.6	398.7	363.8	336.2
37.5°	538.1	579.3	583.6	577.6	541.1	492.6	445.5	409.7	374.0	338.8	310.7
40°	470.5	533.9	547.5	550.0	520.7	468.0	418.7	383.8	348.5	314.1	280.1
42.5°	408.5	488.4	505.4	516.0	494.8	443.8	394.0	355.3	320.5	289.5	255.5
45°	350.2	433.6	461.2	474.8	465.4	416.1	364.7	328.6	296.7	268.2	235.5
47.5°	290.3	374.0	412.7	434.4	434.4	388.1	336.6	300.9	270.3	246.1	217.2
50°	250.4	320.1	360.0	388.5	396.1	359.6	311.1	276.3	247.4	221.0	198.9
52.5°	213.4	275.9	309.0	338.8	360.9	329.0	282.7	251.2	222.7	198.1	180.6
55°	184.5	231.2	261.4	294.1	318.8	298.0	255.0	224.4	199.8	179.4	164.5
57.5°	156.8	197.6	222.3	251.2	277.6	261.8	227.4	201.0	179.4	161.5	148.3
60°	133.5	166.6	185.7	208.3	241.0	230.0	201.5	177.2	159.8	143.7	132.6
62.5°	113.5	139.8	156.0	172.1	201.9	196.8	174.7	156.0	141.1	127.5	118.2
65°	93.1	114.8	127.5	141.5	165.3	167.5	149.6	136.4	122.8	110.9	102.4
67.5°	75.2	92.2	103.7	115.6	134.7	140.7	128.4	117.3	105.8	96.1	88.4
70°	60.8	72.7	81.2	90.5	106.3	113.5	107.1	99.5	90.1	82.0	75.2
72.5°	48.0	55.7	60.8	68.0	80.8	88.0	87.6	80.8	74.0	68.4	62.9
75°	35.3	41.2	45.5	50.2	60.4	67.2	68.9	65.9	59.1	54.8	50.6
77.5°	26.8	30.2	32.3	35.7	42.9	48.9	51.4	50.6	45.9	42.5	39.5
80°	20.4	21.3	22.1	23.4	29.3	34.9	36.6	36.1	33.6	32.3	28.9
82.5°	14.5	14.9	15.3	15.7	17.9	22.5	24.2	25.1	23.0	21.7	18.7
85°	8.5	8.9	8.9	9.8	10.2	11.5	14.5	14.5	14.0	12.3	11.9
87.5°	4.3	4.3	3.8	3.8	4.3	4.7	5.5	6.4	5.5	5.1	4.7
90°	14.7	11.0	9.9	8.8	7.3	5.9	2.9	0.7	2.9	5.9	7.3
92.5°	58.7	38.9	34.8	30.8	25.0	21.3	15.4	11.0	15.4	21.3	25.0
95°	105.7	71.9	63.1	54.3	42.6	36.0	28.6	25.7	28.6	36.0	42.6
97.5°	136.6	93.2	83.3	73.4	60.2	50.7	42.6	38.2	42.6	50.7	60.2
100°	151.2	112.3	102.0	91.8	77.1	65.3	58.7	56.5	58.7	65.3	77.1
102.5°	164.4	129.2	119.0	108.7	93.2	81.5	74.9	73.4	74.9	81.5	93.2
105°	179.9	145.4	135.1	124.8	108.7	97.6	92.5	89.6	92.5	97.6	108.7
107.5°	195.3	161.5	151.2	141.0	124.8	114.5	109.4	107.2	109.4	114.5	124.8
110°	210.7	178.4	167.8	157.1	141.7	132.1	127.7	124.8	127.7	132.1	141.7

TEST NUMBER: P1009916

CATALOG NUMBER: S122RDIP-B290D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	225.4	194.5	183.5	172.5	157.8	149.0	143.9	141.0	143.9	149.0	157.8
115°	240.8	209.2	199.3	189.4	174.7	165.9	161.5	157.8	161.5	165.9	174.7
117.5°	254.7	225.4	215.1	204.8	190.9	182.8	178.4	175.5	178.4	182.8	190.9
120°	269.4	240.8	230.5	220.2	205.6	199.0	194.5	191.6	194.5	199.0	205.6
122.5°	283.4	256.9	246.3	235.7	221.0	213.6	209.2	207.0	209.2	213.6	221.0
125°	297.3	270.9	260.6	250.3	235.7	226.9	222.4	220.2	222.4	226.9	235.7
127.5°	310.5	284.8	274.2	263.6	249.6	240.1	234.2	231.3	234.2	240.1	249.6
130°	322.3	296.6	286.3	276.0	261.4	251.1	243.7	240.8	243.7	251.1	261.4
132.5°	332.6	308.3	298.0	287.8	272.4	261.4	253.3	249.6	253.3	261.4	272.4
135°	342.1	318.6	308.4	298.1	281.2	270.2	261.4	258.4	261.4	270.2	281.2
137.5°	350.2	326.7	317.2	307.6	290.7	279.0	270.2	266.5	270.2	279.0	290.7
140°	356.8	334.8	325.2	315.7	299.5	287.8	279.0	276.0	279.0	287.8	299.5
142.5°	361.9	340.6	331.8	323.0	307.6	295.9	287.8	285.6	287.8	295.9	307.6
145°	367.1	347.2	339.2	331.1	316.4	305.4	298.1	295.1	298.1	305.4	316.4
147.5°	371.5	352.4	345.0	337.7	325.2	314.9	307.6	305.4	307.6	314.9	325.2
150°	374.4	357.5	350.9	344.3	333.3	323.8	317.9	315.7	317.9	323.8	333.3
152.5°	377.3	362.7	356.8	350.9	340.6	332.6	326.7	326.0	326.7	332.6	340.6
155°	380.3	367.8	362.3	356.8	348.7	340.6	336.2	335.5	336.2	340.6	348.7
157.5°	382.5	371.5	366.7	361.9	355.3	348.0	344.3	343.6	344.3	348.0	355.3
160°	384.0	375.1	371.1	367.1	361.2	355.3	352.4	351.7	352.4	355.3	361.2
162.5°	384.7	377.3	374.4	371.5	366.3	361.9	359.0	359.7	359.0	361.9	366.3
165°	385.4	378.8	376.6	374.4	370.7	366.3	364.9	365.6	364.9	366.3	370.7
167.5°	385.4	380.3	378.8	377.3	374.4	371.5	370.0	370.7	370.0	371.5	374.4
170°	384.7	381.0	379.9	378.8	377.3	375.1	374.4	375.9	374.4	375.1	377.3
172.5°	384.0	381.8	381.0	380.3	379.6	377.3	378.1	378.8	378.1	377.3	379.6
175°	383.2	381.8	381.4	381.0	381.0	379.6	380.3	381.0	380.3	379.6	381.0
177.5°	382.5	381.8	381.8	381.8	381.8	380.3	381.0	382.5	381.0	380.3	381.8
180°	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8

TEST NUMBER: P1009916

CATALOG NUMBER: S122RDIP-B290D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6
2.5°	604.8	605.3	606.5	602.7	596.8	594.2	586.6	585.3	584.0	584.0	585.3
5°	591.2	589.5	590.0	582.7	574.2	569.1	558.5	560.2	554.7	551.3	552.1
7.5°	576.4	571.7	571.3	561.9	551.3	541.9	530.9	528.3	523.2	517.3	514.7
10°	557.7	554.3	547.9	537.3	523.7	516.0	501.1	492.2	490.9	482.0	478.6
12.5°	538.5	532.6	526.2	511.3	496.0	483.7	472.7	462.9	456.1	448.4	443.3
15°	516.4	509.2	502.0	486.3	468.4	456.1	439.5	425.0	405.1	389.3	380.4
17.5°	492.2	484.1	474.4	456.9	439.5	422.5	391.9	374.9	360.9	351.5	346.0
20°	467.1	458.2	448.4	431.0	400.8	371.1	354.1	340.9	332.4	323.0	316.2
22.5°	440.8	431.4	420.8	393.6	361.7	340.9	327.7	315.4	303.1	298.0	294.6
25°	416.1	407.6	394.0	357.0	332.0	312.8	298.0	289.9	283.5	276.7	270.3
27.5°	390.6	374.9	355.8	324.7	309.0	289.5	278.8	272.9	261.8	257.2	254.2
30°	360.0	342.6	324.3	302.2	283.9	270.3	260.6	250.8	244.4	239.7	234.6
32.5°	329.0	312.4	300.9	278.0	264.4	250.4	241.0	235.1	225.7	222.7	220.6
35°	302.2	288.2	278.0	259.3	246.5	233.8	227.0	218.1	212.1	206.6	203.2
37.5°	275.9	268.2	257.6	241.9	228.3	218.1	208.7	205.7	197.6	194.7	191.3
40°	257.6	246.1	237.2	223.6	212.1	201.0	195.1	188.3	182.8	178.1	176.8
42.5°	235.5	227.0	221.9	207.0	195.1	188.7	181.5	173.8	169.6	165.8	161.1
45°	218.9	211.2	204.0	192.1	181.5	173.4	167.0	161.9	154.7	153.0	145.8
47.5°	201.5	193.8	188.3	176.4	166.6	159.0	154.3	147.5	141.5	137.7	134.3
50°	184.0	177.7	172.6	162.4	153.9	145.8	139.4	132.6	130.1	123.7	121.6
52.5°	167.5	163.2	157.7	147.9	139.4	132.6	125.8	120.3	116.5	113.1	110.5
55°	153.4	146.6	144.1	133.5	126.2	119.0	113.1	109.7	105.0	102.9	100.7
57.5°	137.7	133.9	129.6	121.6	113.5	106.7	102.4	97.3	94.8	92.2	90.5
60°	124.1	118.6	115.2	108.4	101.2	94.8	91.0	87.1	83.7	81.6	78.2
62.5°	108.4	104.1	102.0	94.8	88.8	82.9	79.5	75.7	73.1	69.3	65.0
65°	94.8	91.4	88.8	82.9	77.4	71.8	68.4	63.8	60.4	58.2	57.8
67.5°	82.9	80.3	76.5	71.0	65.5	61.2	57.4	53.6	53.1	52.3	52.3
70°	69.7	67.2	65.0	59.1	54.4	49.7	48.9	47.6	46.3	45.9	45.1
72.5°	58.2	56.1	53.6	48.5	43.8	42.5	41.7	40.8	39.5	39.1	38.7
75°	47.2	44.2	42.5	37.8	36.6	35.7	34.9	33.6	32.7	32.3	31.5
77.5°	36.1	33.2	33.2	30.6	29.8	28.5	27.6	26.8	26.4	25.5	25.5
80°	25.5	25.5	24.7	23.4	22.1	21.7	20.4	20.0	19.6	20.0	19.1
82.5°	18.7	17.0	17.0	16.2	15.3	14.9	14.0	14.0	13.6	13.6	13.6
85°	10.6	10.6	10.2	9.4	8.9	8.9	8.5	8.5	8.1	8.1	7.7
87.5°	4.3	3.8	4.3	3.8	3.8	3.4	3.4	3.4	3.0	3.4	3.0
90°	8.8	9.9	11.0	14.7	19.8	24.2	25.0	24.2	23.5	22.0	23.5
92.5°	30.8	34.8	38.9	58.7	86.6	111.6	113.1	94.7	74.1	63.1	55.1
95°	54.3	63.1	71.9	105.7	169.6	254.7	287.8	251.8	192.3	147.6	116.7
97.5°	73.4	83.3	93.2	136.6	225.4	362.7	469.1	472.8	393.5	314.2	240.1
100°	91.8	102.0	112.3	151.2	240.8	399.4	580.0	685.7	670.3	579.2	478.7
102.5°	108.7	119.0	129.2	164.4	241.5	385.4	583.6	765.0	851.6	848.7	781.9
105°	124.8	135.1	145.4	179.9	245.2	366.3	544.0	739.3	892.0	974.9	984.5
107.5°	141.0	151.2	161.5	195.3	253.3	356.1	507.3	685.0	848.7	972.0	1044.0
110°	157.1	167.8	178.4	210.7	263.6	353.1	482.3	634.3	789.2	920.6	1014.6

TEST NUMBER: P1009916

CATALOG NUMBER: S122RDIP-B290D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	172.5	183.5	194.5	225.4	274.6	353.9	466.2	599.1	734.9	859.7	961.7
115°	189.4	199.3	209.2	240.8	285.6	356.8	455.2	571.2	692.3	805.4	901.5
117.5°	204.8	215.1	225.4	254.7	297.3	361.2	449.3	552.1	657.1	758.4	847.9
120°	220.2	230.5	240.8	269.4	309.1	365.6	444.2	537.4	632.1	723.1	800.9
122.5°	235.7	246.3	256.9	283.4	319.4	370.7	441.2	524.9	612.3	693.8	766.4
125°	250.3	260.6	270.9	297.3	330.4	375.9	437.5	513.2	593.2	668.8	733.4
127.5°	263.6	274.2	284.8	310.5	340.6	381.0	435.3	502.2	574.1	643.8	705.5
130°	276.0	286.3	296.6	322.3	350.2	386.9	433.9	491.1	555.7	618.9	676.9
132.5°	287.8	298.0	308.3	332.6	359.7	392.8	433.1	482.3	538.1	595.4	647.5
135°	298.1	308.4	318.6	342.1	367.8	397.2	432.4	474.3	522.0	570.4	618.9
137.5°	307.6	317.2	326.7	350.2	374.4	401.6	432.4	468.4	508.8	550.6	590.3
140°	315.7	325.2	334.8	356.8	379.6	404.5	431.7	463.2	496.3	531.5	565.3
142.5°	323.0	331.8	340.6	361.9	384.0	406.7	431.7	458.1	486.0	514.6	542.5
145°	331.1	339.2	347.2	367.1	387.6	408.2	430.2	453.7	476.5	500.7	523.4
147.5°	337.7	345.0	352.4	371.5	389.8	408.9	428.0	449.3	469.1	488.9	507.3
150°	344.3	350.9	357.5	374.4	391.3	408.2	425.8	443.4	461.0	477.2	492.6
152.5°	350.9	356.8	362.7	377.3	392.0	406.7	422.1	438.3	453.0	467.6	480.1
155°	356.8	362.3	367.8	380.3	392.8	405.2	417.7	431.7	445.6	457.4	468.4
157.5°	361.9	366.7	371.5	382.5	392.8	402.3	413.3	425.8	436.8	447.1	456.6
160°	367.1	371.1	375.1	384.0	392.8	400.1	408.9	419.2	428.7	436.8	444.9
162.5°	371.5	374.4	377.3	384.7	392.0	397.9	405.2	413.3	420.7	427.3	433.9
165°	374.4	376.6	378.8	385.4	390.6	395.0	400.1	406.7	412.6	417.7	422.9
167.5°	377.3	378.8	380.3	385.4	389.8	392.0	395.7	400.1	404.5	408.9	412.6
170°	378.8	379.9	381.0	384.7	388.4	389.8	392.0	395.0	398.6	400.8	403.8
172.5°	380.3	381.0	381.8	384.0	386.2	386.9	387.6	389.8	392.0	393.5	395.7
175°	381.0	381.4	381.8	383.2	384.7	384.0	384.7	385.4	387.6	388.4	389.1
177.5°	381.8	381.8	381.8	382.5	384.0	382.5	381.8	382.5	384.0	384.0	384.7
180°	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8

TEST NUMBER: P1009916

CATALOG NUMBER: S122RDIP-B290D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6
2.5°	585.3	584.4	581.9	582.7	581.5	581.5	580.6	580.6	580.6	582.7	581.5
5°	553.4	550.4	547.5	546.2	544.9	543.6	543.6	543.2	547.0	546.2	549.6
7.5°	513.9	513.0	507.1	507.1	505.0	504.1	506.2	506.7	507.1	507.9	510.1
10°	478.6	476.5	468.0	468.8	467.6	465.9	467.1	466.3	469.3	470.1	469.3
12.5°	437.0	433.1	423.8	419.1	414.0	410.2	414.8	411.4	423.3	426.7	436.1
15°	381.7	374.5	368.1	368.1	363.4	360.0	362.1	366.0	368.5	372.3	374.0
17.5°	344.7	341.7	336.6	333.7	332.4	331.1	331.1	332.8	338.3	337.9	341.3
20°	313.3	311.6	309.0	305.2	303.9	303.1	303.1	303.1	306.9	310.3	312.4
22.5°	291.6	290.3	288.6	283.5	281.0	280.1	282.2	283.5	286.5	289.0	291.2
25°	269.9	266.9	264.0	262.3	261.0	261.0	261.8	262.3	263.5	264.8	267.4
27.5°	252.1	249.9	245.7	241.0	241.0	239.7	240.6	241.4	244.4	248.7	250.8
30°	232.1	231.7	230.0	228.3	226.6	225.7	227.4	228.7	229.1	231.2	231.2
32.5°	217.6	214.6	211.7	210.0	209.1	208.7	209.1	210.8	210.8	213.4	216.4
35°	203.2	201.5	198.5	195.5	194.7	192.5	194.2	195.9	198.9	200.2	201.5
37.5°	187.4	185.3	184.0	183.2	181.5	181.9	180.6	183.2	185.7	185.3	186.2
40°	175.5	171.7	167.9	167.5	167.0	166.6	166.6	167.0	168.7	170.4	173.0
42.5°	160.2	159.0	155.6	152.2	151.3	150.5	149.6	151.3	154.7	157.7	159.0
45°	144.5	142.8	142.0	139.4	137.7	137.3	136.4	138.6	141.5	142.8	143.7
47.5°	130.1	129.6	127.1	127.5	126.2	126.7	126.2	127.5	127.5	128.8	129.6
50°	120.3	119.0	117.7	116.9	115.6	115.6	115.2	115.6	117.3	119.0	118.6
52.5°	110.5	108.4	108.0	107.5	106.7	107.5	106.3	106.7	108.4	109.2	108.8
55°	99.0	98.6	97.8	96.9	96.5	96.1	96.1	96.1	97.8	99.0	99.5
57.5°	90.1	88.0	86.3	86.3	84.6	84.2	85.0	85.4	86.7	87.6	88.4
60°	77.8	76.9	74.4	73.1	70.6	70.1	70.1	71.8	74.0	76.9	77.8
62.5°	64.6	63.3	62.9	62.9	62.9	62.9	62.9	62.9	62.9	63.3	63.3
65°	57.4	57.8	57.4	57.0	57.4	57.4	57.0	57.0	57.0	57.4	57.8
67.5°	51.4	51.0	51.4	51.0	50.6	50.6	50.2	50.6	51.0	51.4	51.4
70°	44.6	44.6	44.2	44.6	44.2	43.8	43.4	43.4	44.2	44.6	44.6
72.5°	38.3	38.3	37.8	37.8	37.0	37.0	37.4	37.0	37.0	38.3	38.3
75°	31.9	31.5	31.0	31.0	30.6	30.6	30.6	30.2	31.0	31.0	31.5
77.5°	25.1	25.1	25.1	24.7	24.7	24.2	24.2	24.7	24.7	24.7	25.1
80°	19.1	19.1	19.1	18.7	18.3	18.3	18.3	18.3	18.3	18.7	18.3
82.5°	13.2	13.2	13.2	13.2	13.2	12.8	12.8	12.8	13.2	13.2	12.8
85°	8.1	7.7	8.1	8.1	7.7	8.1	7.7	7.7	7.2	7.2	7.7
87.5°	3.4	3.0	2.6	2.6	3.0	2.6	2.6	2.6	3.0	2.6	2.6
90°	23.8	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	23.8
92.5°	52.2	49.2	48.5	45.5	46.3	44.8	46.3	45.5	48.5	49.2	52.2
95°	108.6	100.6	91.0	85.2	83.0	83.7	83.0	85.2	91.0	100.6	108.6
97.5°	218.0	196.0	167.4	152.7	144.6	140.2	144.6	152.7	167.4	196.0	218.0
100°	434.2	389.8	328.9	297.3	276.0	262.8	276.0	297.3	328.9	389.8	434.2
102.5°	734.2	686.4	618.9	559.4	531.5	512.4	531.5	559.4	618.9	686.4	734.2
105°	972.4	960.3	914.7	869.2	837.7	827.4	837.7	869.2	914.7	960.3	972.4
107.5°	1058.6	1073.3	1072.6	1066.0	1056.4	1039.5	1056.4	1066.0	1072.6	1073.3	1058.6
110°	1044.7	1074.8	1106.4	1120.3	1126.9	1126.2	1126.9	1120.3	1106.4	1074.8	1044.7

TEST NUMBER: P1009916

CATALOG NUMBER: S122RDIP-B290D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	997.3	1032.9	1079.9	1105.6	1119.6	1124.7	1119.6	1105.6	1079.9	1032.9	997.3
115°	939.3	977.1	1029.3	1063.0	1082.1	1088.7	1082.1	1063.0	1029.3	977.1	939.3
117.5°	883.9	919.9	973.5	1009.4	1029.3	1034.4	1029.3	1009.4	973.5	919.9	883.9
120°	834.4	867.8	919.1	953.7	974.9	982.3	974.9	953.7	919.1	867.8	834.4
122.5°	795.8	825.2	870.0	903.7	922.1	928.0	922.1	903.7	870.0	825.2	795.8
125°	761.0	788.5	831.0	858.9	877.3	883.2	877.3	858.9	831.0	788.5	761.0
127.5°	731.2	756.9	794.3	820.8	836.9	841.3	836.9	820.8	794.3	756.9	731.2
130°	701.1	725.3	761.3	786.3	800.9	806.8	800.9	786.3	761.3	725.3	701.1
132.5°	669.9	692.3	727.5	752.5	765.7	770.8	765.7	752.5	727.5	692.3	669.9
135°	639.4	660.0	691.6	715.8	729.0	731.9	729.0	715.8	691.6	660.0	639.4
137.5°	608.6	627.0	657.1	678.3	690.1	694.5	690.1	678.3	657.1	627.0	608.6
140°	581.4	597.6	621.1	640.2	651.2	655.6	651.2	640.2	621.1	597.6	581.4
142.5°	555.4	568.2	590.3	607.1	616.7	616.7	616.7	607.1	590.3	568.2	555.4
145°	534.0	544.7	562.4	574.8	582.2	584.4	582.2	574.8	562.4	544.7	534.0
147.5°	515.4	523.4	538.9	549.1	554.3	555.7	554.3	549.1	538.9	523.4	515.4
150°	499.2	505.8	516.8	525.6	530.1	530.8	530.1	525.6	516.8	505.8	499.2
152.5°	485.6	491.1	499.2	506.6	509.5	509.5	509.5	506.6	499.2	491.1	485.6
155°	472.4	476.5	484.5	489.7	492.6	491.1	492.6	489.7	484.5	476.5	472.4
157.5°	459.9	463.2	469.1	473.5	475.0	475.0	475.0	473.5	469.1	463.2	459.9
160°	447.4	450.0	455.2	458.8	459.6	459.6	459.6	458.8	455.2	450.0	447.4
162.5°	435.7	437.5	442.7	444.9	445.6	444.9	445.6	444.9	442.7	437.5	435.7
165°	424.4	425.8	428.7	431.7	431.7	430.9	431.7	431.7	428.7	425.8	424.4
167.5°	414.0	415.5	417.0	418.5	418.5	417.7	418.5	418.5	417.0	415.5	414.0
170°	404.5	405.2	406.0	408.2	407.4	406.0	407.4	408.2	406.0	405.2	404.5
172.5°	396.0	396.4	397.2	397.9	397.2	396.4	397.2	397.9	397.2	396.4	396.0
175°	389.5	389.8	389.8	390.6	389.8	388.4	389.8	390.6	389.8	389.8	389.5
177.5°	384.7	384.7	384.7	384.7	384.0	382.5	384.0	384.7	384.7	384.7	384.7
180°	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8

TEST NUMBER: P1009916

CATALOG NUMBER: S122RDIP-B290D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6	611.6
2.5°	582.7	584.9	584.0	579.3	584.0	585.3	587.8	590.4	592.1	594.6	596.8
5°	546.2	550.4	553.0	550.4	558.9	560.2	566.2	569.6	574.7	578.9	582.3
7.5°	511.8	515.2	520.3	521.1	526.2	532.2	540.7	549.2	557.2	561.5	565.3
10°	474.8	480.7	488.4	486.7	494.3	503.7	512.6	526.2	533.0	540.7	547.5
12.5°	437.8	441.6	451.8	455.2	466.3	473.5	485.8	494.3	511.3	520.3	526.2
15°	373.2	388.9	401.7	417.0	431.4	445.0	456.1	471.4	486.3	493.1	502.8
17.5°	343.9	351.1	358.7	366.4	385.1	409.3	428.9	445.5	458.2	467.1	478.6
20°	313.3	320.5	329.0	336.2	347.7	365.1	389.3	417.8	433.1	442.5	453.5
22.5°	291.6	298.4	303.9	310.3	319.2	332.0	350.2	385.5	405.9	417.4	427.2
25°	268.2	276.7	282.7	287.3	294.6	308.6	323.5	343.4	380.0	388.9	402.5
27.5°	252.1	254.6	261.4	268.6	275.9	283.5	298.8	315.8	340.5	360.0	376.6
30°	232.9	239.3	245.7	248.7	255.0	266.1	275.4	293.7	312.8	328.1	348.1
32.5°	218.5	222.3	226.6	233.8	239.7	247.4	256.7	272.0	288.2	298.0	313.3
35°	202.3	204.9	213.8	216.8	222.7	230.4	239.7	251.6	269.1	276.7	287.8
37.5°	187.0	193.0	195.5	202.3	207.8	215.5	222.3	235.9	247.4	256.3	266.5
40°	175.1	177.7	182.3	188.3	193.0	198.9	207.4	217.2	229.5	236.8	245.7
42.5°	160.7	162.8	168.7	172.1	179.8	185.3	190.4	202.3	213.4	218.9	227.8
45°	144.9	150.0	153.9	160.7	164.9	171.7	178.1	186.6	196.8	203.2	208.3
47.5°	131.3	136.4	140.3	146.6	153.4	156.4	163.2	172.1	181.5	186.6	193.8
50°	120.3	122.0	129.2	132.2	139.4	145.4	150.0	157.7	167.9	170.9	176.8
52.5°	109.7	110.9	115.6	119.4	125.8	130.9	136.9	144.1	152.6	157.3	161.9
55°	100.3	101.2	103.3	107.5	111.8	118.2	123.7	130.5	137.7	142.8	147.1
57.5°	89.7	91.4	93.1	95.6	99.9	105.8	111.8	118.2	124.1	127.5	133.0
60°	77.4	79.9	82.9	85.9	88.8	93.1	99.9	105.8	111.4	114.3	118.6
62.5°	64.2	69.3	71.8	75.2	77.8	81.6	86.7	93.5	97.3	101.2	104.6
65°	57.8	58.2	58.7	62.1	66.7	70.6	75.2	80.3	86.3	88.8	91.4
67.5°	51.4	51.9	52.7	53.1	54.8	59.1	64.2	69.7	74.4	76.1	78.6
70°	45.1	45.1	46.8	47.2	47.6	48.0	52.3	57.8	62.1	64.2	67.2
72.5°	38.3	38.7	39.5	40.0	40.8	41.7	42.9	45.9	51.0	53.1	56.5
75°	31.5	31.9	32.3	32.7	34.0	34.4	35.7	37.4	39.5	42.1	44.2
77.5°	25.1	25.1	25.5	26.4	27.2	27.6	28.9	29.8	30.6	31.9	33.6
80°	18.7	19.1	19.1	20.0	20.0	20.4	20.8	22.1	23.0	23.8	24.7
82.5°	12.8	13.6	13.6	13.6	14.0	14.5	14.9	14.9	15.7	16.2	17.4
85°	7.7	8.1	8.1	8.1	7.7	8.5	8.5	8.9	8.9	8.9	9.4
87.5°	3.0	2.6	3.0	3.0	3.0	3.4	3.0	3.0	3.4	3.8	3.8
90°	23.5	22.0	23.5	24.2	25.0	24.2	19.8	14.7	11.0	9.9	8.8
92.5°	55.1	63.1	74.1	94.7	113.1	111.6	86.6	58.7	38.9	34.8	30.8
95°	116.7	147.6	192.3	251.8	287.8	254.7	169.6	105.7	71.9	63.1	54.3
97.5°	240.1	314.2	393.5	472.8	469.1	362.7	225.4	136.6	93.2	83.3	73.4
100°	478.7	579.2	670.3	685.7	580.0	399.4	240.8	151.2	112.3	102.0	91.8
102.5°	781.9	848.7	851.6	765.0	583.6	385.4	241.5	164.4	129.2	119.0	108.7
105°	984.5	974.9	892.0	739.3	544.0	366.3	245.2	179.9	145.4	135.1	124.8
107.5°	1044.0	972.0	848.7	685.0	507.3	356.1	253.3	195.3	161.5	151.2	141.0
110°	1014.6	920.6	789.2	634.3	482.3	353.1	263.6	210.7	178.4	167.8	157.1

TEST NUMBER: P1009916

CATALOG NUMBER: S122RDIP-B290D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	961.7	859.7	734.9	599.1	466.2	353.9	274.6	225.4	194.5	183.5	172.5
115°	901.5	805.4	692.3	571.2	455.2	356.8	285.6	240.8	209.2	199.3	189.4
117.5°	847.9	758.4	657.1	552.1	449.3	361.2	297.3	254.7	225.4	215.1	204.8
120°	800.9	723.1	632.1	537.4	444.2	365.6	309.1	269.4	240.8	230.5	220.2
122.5°	766.4	693.8	612.3	524.9	441.2	370.7	319.4	283.4	256.9	246.3	235.7
125°	733.4	668.8	593.2	513.2	437.5	375.9	330.4	297.3	270.9	260.6	250.3
127.5°	705.5	643.8	574.1	502.2	435.3	381.0	340.6	310.5	284.8	274.2	263.6
130°	676.9	618.9	555.7	491.1	433.9	386.9	350.2	322.3	296.6	286.3	276.0
132.5°	647.5	595.4	538.1	482.3	433.1	392.8	359.7	332.6	308.3	298.0	287.8
135°	618.9	570.4	522.0	474.3	432.4	397.2	367.8	342.1	318.6	308.4	298.1
137.5°	590.3	550.6	508.8	468.4	432.4	401.6	374.4	350.2	326.7	317.2	307.6
140°	565.3	531.5	496.3	463.2	431.7	404.5	379.6	356.8	334.8	325.2	315.7
142.5°	542.5	514.6	486.0	458.1	431.7	406.7	384.0	361.9	340.6	331.8	323.0
145°	523.4	500.7	476.5	453.7	430.2	408.2	387.6	367.1	347.2	339.2	331.1
147.5°	507.3	488.9	469.1	449.3	428.0	408.9	389.8	371.5	352.4	345.0	337.7
150°	492.6	477.2	461.0	443.4	425.8	408.2	391.3	374.4	357.5	350.9	344.3
152.5°	480.1	467.6	453.0	438.3	422.1	406.7	392.0	377.3	362.7	356.8	350.9
155°	468.4	457.4	445.6	431.7	417.7	405.2	392.8	380.3	367.8	362.3	356.8
157.5°	456.6	447.1	436.8	425.8	413.3	402.3	392.8	382.5	371.5	366.7	361.9
160°	444.9	436.8	428.7	419.2	408.9	400.1	392.8	384.0	375.1	371.1	367.1
162.5°	433.9	427.3	420.7	413.3	405.2	397.9	392.0	384.7	377.3	374.4	371.5
165°	422.9	417.7	412.6	406.7	400.1	395.0	390.6	385.4	378.8	376.6	374.4
167.5°	412.6	408.9	404.5	400.1	395.7	392.0	389.8	385.4	380.3	378.8	377.3
170°	403.8	400.8	398.6	395.0	392.0	389.8	388.4	384.7	381.0	379.9	378.8
172.5°	395.7	393.5	392.0	389.8	387.6	386.9	386.2	384.0	381.8	381.0	380.3
175°	389.1	388.4	387.6	385.4	384.7	384.0	384.7	383.2	381.8	381.4	381.0
177.5°	384.7	384.0	384.0	382.5	381.8	382.5	384.0	382.5	381.8	381.8	381.8
180°	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8

TEST NUMBER: P1009916

CATALOG NUMBER: S122RDIP-B290D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	611.6	611.6	611.6	611.6
2.5°	600.6	599.3	607.0	615.5
5°	588.3	590.4	600.2	612.1
7.5°	575.5	580.2	591.7	607.4
10°	557.7	566.2	583.6	599.7
12.5°	540.2	551.7	568.3	587.4
15°	520.7	533.4	553.8	576.8
17.5°	499.0	513.5	537.3	562.3
20°	476.1	495.2	520.3	547.5
22.5°	450.6	473.5	499.4	529.6
25°	425.9	451.0	476.9	511.8
27.5°	401.7	426.3	455.2	490.5
30°	377.4	400.0	431.0	468.8
32.5°	351.5	374.9	407.6	446.3
35°	327.7	351.1	381.7	419.9
37.5°	302.2	327.3	356.6	396.1
40°	272.5	301.8	330.3	368.1
42.5°	247.8	278.8	306.5	342.2
45°	228.3	257.6	280.5	315.4
47.5°	210.0	233.8	257.2	289.5
50°	192.5	210.8	235.1	264.0
52.5°	174.7	190.4	211.2	238.5
55°	158.5	173.4	192.1	212.9
57.5°	143.7	154.3	173.0	191.7
60°	127.1	138.1	152.6	168.3
62.5°	113.1	121.6	135.2	148.3
65°	98.2	106.3	116.5	128.8
67.5°	84.6	91.8	99.9	109.7
70°	72.3	77.8	83.7	92.2
72.5°	59.1	65.0	70.6	77.4
75°	48.5	51.0	55.7	60.4
77.5°	37.4	40.8	43.4	47.2
80°	26.8	29.8	30.6	33.6
82.5°	17.9	19.6	21.3	22.1
85°	10.2	11.1	12.8	13.2
87.5°	3.8	4.3	5.1	6.0
90°	7.3	5.9	2.9	0.7
92.5°	25.0	21.3	15.4	11.0
95°	42.6	36.0	28.6	25.7
97.5°	60.2	50.7	42.6	38.2
100°	77.1	65.3	58.7	56.5
102.5°	93.2	81.5	74.9	73.4
105°	108.7	97.6	92.5	89.6
107.5°	124.8	114.5	109.4	107.2
110°	141.7	132.1	127.7	124.8

TEST NUMBER: P1009916

CATALOG NUMBER: S122RDIP-B290D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	157.8	149.0	143.9	141.0
115°	174.7	165.9	161.5	157.8
117.5°	190.9	182.8	178.4	175.5
120°	205.6	199.0	194.5	191.6
122.5°	221.0	213.6	209.2	207.0
125°	235.7	226.9	222.4	220.2
127.5°	249.6	240.1	234.2	231.3
130°	261.4	251.1	243.7	240.8
132.5°	272.4	261.4	253.3	249.6
135°	281.2	270.2	261.4	258.4
137.5°	290.7	279.0	270.2	266.5
140°	299.5	287.8	279.0	276.0
142.5°	307.6	295.9	287.8	285.6
145°	316.4	305.4	298.1	295.1
147.5°	325.2	314.9	307.6	305.4
150°	333.3	323.8	317.9	315.7
152.5°	340.6	332.6	326.7	326.0
155°	348.7	340.6	336.2	335.5
157.5°	355.3	348.0	344.3	343.6
160°	361.2	355.3	352.4	351.7
162.5°	366.3	361.9	359.0	359.7
165°	370.7	366.3	364.9	365.6
167.5°	374.4	371.5	370.0	370.7
170°	377.3	375.1	374.4	375.9
172.5°	379.6	377.3	378.1	378.8
175°	381.0	379.6	380.3	381.0
177.5°	381.8	380.3	381.0	382.5
180°	381.8	381.8	381.8	381.8

(END OF REPORT)