

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009922

Luminaire Tested: S122RDIP-B290D925UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009922
REPORT IS A COMBINATION OF REPORTS P988180 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B290D925UB27-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4641.0 lumens
Efficiency: N/A
Efficacy: 111.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009922

CATALOG NUMBER: S122RDIP-B290D925UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1009922

CATALOG NUMBER: S122RDIP-B290D925UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32
1	92	88	85	81	82	79	76	73	60	59	57	44	43	42	29	28	27
2	84	77	72	67	75	69	64	60	53	50	48	39	37	35	26	25	24
3	77	68	62	56	68	61	55	51	47	44	40	35	32	30	23	22	21
4	71	61	53	48	63	54	48	43	42	38	35	31	28	26	21	19	18
5	65	54	47	41	57	48	42	37	38	33	30	28	25	23	19	17	16
6	60	48	41	36	53	44	37	32	34	30	26	26	23	20	17	16	14
7	55	44	36	31	49	39	33	28	31	27	23	23	20	18	16	14	13
8	51	40	32	27	46	36	30	25	28	24	21	21	18	16	15	13	12
9	48	36	29	24	42	33	27	22	26	22	18	20	17	14	14	12	11
10	44	33	26	22	40	30	24	20	24	20	17	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9984	9984	9984	9984
5°	10008	10604	10043	8472
10°	9898	11209	9968	6996
15°	9683	11212	9847	5256
20°	9425	9268	9629	4336
25°	9110	5791	9307	3688
30°	8712	3709	8948	3175
35°	8225	2850	8491	2718
40°	7683	2395	8011	2377
45°	7102	2038	7399	1996
50°	6509	1733	6813	1726
55°	5851	1506	6166	1486
60°	5268	1148	5547	1134
65°	4721	865	5002	980
70°	4119	690	4443	798
75°	3479	528	3798	605
80°	2762	359	2978	395
85°	1921	186	2105	195

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 9134 cd/sqm

TEST NUMBER: P1009922

CATALOG NUMBER: S122RDIP-B290D925UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.8	1.3
10°-20°	167.0	3.6
20°-30°	214.9	4.6
30°-40°	203.9	4.4
40°-50°	174.7	3.8
50°-60°	133.1	2.9
60°-70°	83.9	1.8
70°-80°	41.9	0.9
80°-90°	14.0	0.3
90°-100°	198.6	4.3
100°-110°	699.4	15.1
110°-120°	734.5	15.8
120°-130°	604.3	13.0
130°-140°	485.4	10.5
140°-150°	366.7	7.9
150°-160°	257.8	5.6
160°-170°	151.7	3.3
170°-180°	49.4	1.1
0°-30°	441.7	9.5
0°-40°	645.6	13.9
0°-60°	953.4	20.5
0°-90°	1093.3	23.6
90°-120°	1632.5	35.2
90°-150°	3088.8	66.6
90°-180°	3548.0	76.4
0°-180°	4641.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	631	631	631	631	631	
5°	631	702	633	561	631	60
15°	595	792	605	371	595	167
25°	528	422	539	269	528	242
35°	433	208	447	199	433	271
45°	325	145	339	142	325	251
55°	220	100	231	99	220	198
65°	133	52	141	59	133	132
75°	62	28	68	32	62	67
85°	14	8	15	8	14	15
90°	1	32	1	32	1	3
95°	34	112	34	112	34	35
105°	120	1104	120	1104	120	127
115°	211	1453	211	1453	211	209
125°	294	1179	294	1179	294	261
135°	345	977	345	977	345	266
145°	394	780	394	780	394	247
155°	448	655	448	655	448	206
165°	488	575	488	575	488	138
175°	508	518	508	518	508	48
180°	509	509	509	509	509	

TEST NUMBER: P1009922

CATALOG NUMBER: S122RDIP-B290D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	634.7	637.3	638.6	640.4	644.3	647.0	650.9	651.8	651.3	653.1	648.3
5°	631.2	636.9	642.1	646.5	653.5	657.9	662.7	668.4	669.8	676.3	672.4
7.5°	626.4	634.7	642.1	650.9	661.4	667.1	674.6	683.3	687.3	695.2	697.4
10°	618.5	630.3	643.0	652.2	666.7	676.8	683.8	697.8	707.0	718.8	717.1
12.5°	605.8	621.1	638.2	653.5	672.4	679.0	692.1	706.6	718.4	729.4	739.0
15°	594.8	612.3	631.2	650.0	671.5	683.8	696.9	715.8	728.5	747.8	756.1
17.5°	579.9	602.3	624.6	645.6	671.1	685.1	701.3	719.7	738.6	757.0	763.6
20°	564.6	588.7	612.8	641.3	670.2	683.8	700.4	723.2	741.6	756.1	756.1
22.5°	546.1	575.5	603.1	630.3	661.9	681.6	698.7	725.4	738.6	741.6	729.8
25°	527.7	557.1	587.3	621.1	657.0	674.6	693.9	718.8	723.2	711.0	680.3
27.5°	505.8	538.7	572.9	609.3	647.0	668.9	686.4	703.1	694.7	661.9	614.1
30°	483.5	519.0	557.5	592.2	637.8	657.9	672.8	677.6	651.3	597.9	536.1
32.5°	460.2	494.9	535.6	577.3	623.3	642.6	652.2	639.5	591.3	523.8	448.4
35°	433.1	472.1	514.6	558.0	603.6	618.0	623.7	592.6	530.8	443.6	368.6
37.5°	408.5	447.5	493.1	537.4	581.6	589.5	583.8	535.2	456.7	370.4	297.2
40°	379.6	421.2	465.9	515.5	551.8	554.0	540.0	476.9	379.6	298.5	253.3
42.5°	352.8	394.9	439.6	490.0	517.7	510.2	491.4	408.5	316.9	257.3	220.9
45°	325.2	365.1	413.3	458.0	477.8	460.2	431.7	343.6	266.1	221.4	193.3
47.5°	298.5	335.8	383.5	426.5	430.0	410.3	376.5	288.0	230.6	194.6	171.8
50°	272.2	309.5	354.2	389.7	386.2	359.0	320.8	250.3	200.3	171.8	153.0
52.5°	245.9	279.6	323.0	351.1	336.2	309.9	272.2	212.1	174.9	149.9	135.4
55°	219.6	251.2	288.4	311.6	288.0	257.7	231.0	181.9	151.7	131.5	120.5
57.5°	197.7	222.7	256.9	270.9	242.4	218.7	195.5	156.5	131.5	117.0	104.3
60°	173.6	196.4	224.4	232.7	203.4	184.1	164.4	132.4	112.6	99.9	91.6
62.5°	153.0	171.8	193.3	193.3	167.4	153.0	138.1	110.9	94.7	84.6	80.7
65°	132.8	146.4	161.7	160.0	138.1	125.4	113.5	91.6	79.3	72.3	68.4
67.5°	113.1	123.6	133.7	127.6	111.8	100.8	89.9	74.1	65.7	60.9	55.7
70°	95.1	103.4	108.7	103.0	87.2	78.0	70.1	59.6	53.0	46.9	43.8
72.5°	79.8	83.3	85.0	78.0	64.9	59.6	53.9	46.5	40.8	37.7	36.8
75°	62.2	65.3	64.0	58.7	47.8	43.8	39.4	34.2	32.9	31.1	30.2
77.5°	48.7	48.7	46.5	41.6	34.2	31.1	29.4	26.7	25.4	25.0	24.1
80°	34.6	34.2	32.9	27.6	23.2	21.5	21.5	19.7	19.3	18.4	18.4
82.5°	22.8	22.8	21.0	16.7	15.3	14.9	14.5	13.6	13.6	13.1	13.1
85°	13.6	12.7	10.5	9.2	8.8	8.8	8.3	7.9	8.3	7.9	7.9
87.5°	6.1	4.8	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
90°	1.0	3.9	7.8	9.8	11.8	13.2	14.7	19.6	26.5	32.3	33.3
92.5°	14.7	20.6	28.4	33.3	41.1	46.5	51.9	78.4	115.6	148.9	150.9
95°	34.3	38.2	48.0	56.8	72.5	84.2	96.0	141.1	226.3	340.0	384.0
97.5°	50.9	56.8	67.6	80.3	98.0	111.2	124.4	182.2	300.8	484.0	626.0
100°	75.4	78.4	87.2	102.9	122.5	136.2	149.9	201.8	321.3	532.9	774.0
102.5°	98.0	99.9	108.7	124.4	145.0	158.7	172.4	219.4	322.3	514.3	778.8
105°	119.5	123.4	130.3	145.0	166.5	180.2	194.0	240.0	327.2	488.9	725.9
107.5°	143.0	146.0	152.8	166.5	188.1	201.8	215.5	260.6	338.0	475.1	677.0
110°	166.5	170.5	176.3	189.1	209.7	223.9	238.1	281.2	351.7	471.2	643.7

TEST NUMBER: P1009922

CATALOG NUMBER: S122RDIP-B290D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	188.1	192.0	198.9	210.6	230.2	244.9	259.6	300.8	366.4	472.2	622.1
115°	210.6	215.5	221.4	233.2	252.8	266.0	279.2	321.3	381.1	476.1	607.4
117.5°	234.1	238.1	243.9	254.7	273.3	287.0	300.8	340.0	396.8	482.0	599.6
120°	255.7	259.6	265.5	274.3	293.9	307.6	321.3	359.5	412.4	487.9	592.7
122.5°	276.3	279.2	285.1	294.9	314.5	328.7	342.9	378.2	426.2	494.7	588.8
125°	293.9	296.8	302.7	314.5	334.1	347.8	361.5	396.8	440.9	501.6	583.9
127.5°	308.6	312.5	320.4	333.1	351.7	365.9	380.1	414.4	454.6	508.5	581.0
130°	321.3	325.3	335.1	348.8	368.4	382.1	395.8	430.1	467.3	516.3	579.0
132.5°	333.1	338.0	348.8	363.5	384.0	397.8	411.5	443.8	480.0	524.1	578.0
135°	344.8	348.8	360.5	375.2	397.8	411.5	425.2	456.5	490.8	530.0	577.0
137.5°	355.6	360.5	372.3	388.0	410.5	423.2	436.0	467.3	499.6	535.9	577.0
140°	368.4	372.3	384.0	399.7	421.3	434.0	446.7	476.1	506.5	539.8	576.1
142.5°	381.1	384.0	394.8	410.5	431.1	442.8	454.6	483.0	512.4	542.7	576.1
145°	393.8	397.8	407.5	422.2	441.8	452.6	463.4	489.8	517.3	544.7	574.1
147.5°	407.5	410.5	420.3	434.0	450.7	460.4	470.2	495.7	520.2	545.7	571.2
150°	421.3	424.2	432.0	444.8	459.5	468.3	477.1	499.6	522.2	544.7	568.2
152.5°	435.0	436.0	443.8	454.6	468.3	476.2	484.0	503.6	523.2	542.7	563.3
155°	447.7	448.7	454.6	465.4	476.1	483.4	490.8	507.5	524.1	540.8	557.4
157.5°	458.5	459.5	464.4	474.2	483.0	489.4	495.7	510.4	524.1	536.9	551.6
160°	469.3	470.2	474.2	482.0	489.8	495.2	500.6	512.4	524.1	533.9	545.7
162.5°	480.0	479.1	483.0	488.9	495.7	499.6	503.6	513.4	523.2	531.0	540.8
165°	487.9	486.9	488.9	494.7	499.6	502.6	505.5	514.3	521.2	527.1	533.9
167.5°	494.7	493.8	495.7	499.6	503.6	505.6	507.5	514.3	520.2	523.2	528.1
170°	501.6	499.6	500.6	503.6	505.5	507.0	508.5	513.4	518.3	520.2	523.2
172.5°	505.5	504.5	503.6	506.5	507.5	508.4	509.4	512.4	515.3	516.3	517.3
175°	508.5	507.5	506.5	508.5	508.5	509.0	509.4	511.4	513.4	512.4	513.4
177.5°	510.4	508.5	507.5	509.4	509.4	509.4	509.4	510.4	512.4	510.4	509.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P1009922

CATALOG NUMBER: S122RDIP-B290D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	653.1	654.0	655.3	661.4	662.3	664.1	663.2	663.2	663.6	662.7	663.2
5°	681.1	682.5	689.0	696.5	698.2	696.5	698.7	701.7	701.7	701.7	700.9
7.5°	707.4	712.3	719.7	730.7	732.9	735.1	739.0	736.4	737.3	741.2	739.9
10°	732.9	739.9	748.2	757.4	762.2	765.3	767.1	771.0	780.2	769.7	773.6
12.5°	757.0	767.1	775.8	785.9	789.4	793.4	794.7	798.2	798.2	797.7	800.8
15°	772.8	782.0	789.9	796.4	797.3	796.4	795.5	796.0	797.3	792.0	795.1
17.5°	776.3	777.1	779.8	777.1	777.6	768.4	763.1	761.8	749.5	750.0	760.0
20°	759.2	744.3	740.3	725.9	717.1	693.4	692.5	686.0	660.1	668.0	666.2
22.5°	712.3	686.8	653.1	636.4	628.1	603.1	583.8	570.3	561.0	551.8	547.9
25°	650.5	609.3	561.5	528.6	523.8	500.6	465.1	448.4	428.7	422.5	433.1
27.5°	570.7	517.2	463.3	412.9	403.7	382.7	364.7	352.8	330.1	328.7	329.6
30°	462.4	408.5	363.4	330.5	307.7	298.1	286.2	277.5	268.3	271.8	272.6
32.5°	380.0	328.7	286.7	269.1	258.6	252.5	242.4	236.7	232.7	231.4	231.0
35°	302.0	267.8	249.0	231.9	225.7	221.4	213.9	211.3	207.8	208.2	208.2
37.5°	258.6	230.1	216.1	207.3	201.6	199.4	194.6	192.0	189.8	188.9	190.2
40°	223.1	203.4	194.6	186.7	181.9	181.0	178.4	175.3	172.7	173.1	174.5
42.5°	197.2	185.8	175.3	169.2	165.7	164.4	162.2	160.0	160.0	158.7	158.2
45°	176.6	167.4	158.7	153.0	150.8	149.0	146.4	146.0	144.2	144.6	145.1
47.5°	158.2	150.8	144.2	138.5	136.3	135.9	133.2	131.5	131.5	131.1	130.6
50°	141.6	134.1	128.4	125.4	122.3	121.4	121.0	120.5	119.7	119.7	120.1
52.5°	128.0	120.5	116.2	113.5	111.8	110.9	110.9	110.5	110.5	110.5	110.0
55°	113.1	106.9	103.4	102.6	101.7	101.3	100.8	99.9	99.5	100.4	99.5
57.5°	99.1	96.9	93.8	92.9	90.7	90.7	89.4	88.5	87.7	88.5	88.5
60°	88.1	85.0	83.3	80.7	78.9	77.1	75.0	74.5	73.6	73.2	72.8
62.5°	76.7	74.1	69.7	65.7	63.1	61.4	60.5	60.0	60.0	59.6	59.6
65°	64.0	57.9	55.7	54.4	53.9	53.5	52.6	52.2	52.6	52.2	52.6
67.5°	50.0	49.1	47.8	46.9	46.5	46.0	46.0	45.6	45.6	45.6	45.6
70°	43.4	41.2	40.8	39.9	39.9	39.4	39.4	39.4	39.4	39.0	39.9
72.5°	35.9	34.6	34.2	33.8	33.8	33.8	33.3	33.3	33.3	32.9	33.3
75°	29.4	28.9	28.1	28.1	27.6	28.1	27.6	27.6	27.2	27.6	27.6
77.5°	23.7	23.2	22.8	22.8	22.4	22.4	22.4	22.4	22.4	22.4	22.8
80°	18.0	17.5	17.1	17.5	17.1	17.5	17.1	17.1	17.5	17.1	17.1
82.5°	13.1	12.7	12.7	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3
85°	7.9	7.5	7.5	7.9	7.5	7.9	7.5	7.5	7.5	7.9	7.9
87.5°	3.5	3.9	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.9
90°	32.3	31.3	29.4	31.3	31.8	32.3	32.3	32.3	32.3	32.3	32.3
92.5°	126.4	98.9	84.3	73.5	69.6	65.6	64.7	60.7	61.7	59.8	61.7
95°	336.0	256.7	196.9	155.8	145.0	134.2	121.5	113.6	110.7	111.7	110.7
97.5°	630.9	525.1	419.3	320.4	291.0	261.6	223.4	203.8	193.0	187.1	193.0
100°	915.0	894.5	773.0	638.8	579.5	520.2	438.9	396.8	368.4	350.7	368.4
102.5°	1020.8	1136.4	1132.5	1043.4	979.7	916.0	825.9	746.5	709.3	683.8	709.3
105°	986.5	1190.3	1301.0	1313.8	1297.6	1281.4	1220.7	1159.9	1117.8	1104.1	1117.8
107.5°	914.0	1132.5	1297.1	1393.1	1412.7	1432.3	1431.3	1422.5	1409.8	1387.2	1409.8
110°	846.4	1053.2	1228.5	1353.9	1394.1	1434.3	1476.4	1495.0	1503.8	1502.8	1503.8

TEST NUMBER: P1009922

CATALOG NUMBER: S122RDIP-B290D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	799.4	980.7	1147.2	1283.4	1330.9	1378.4	1441.1	1475.4	1494.0	1500.9	1494.0
115°	762.2	923.8	1074.7	1203.1	1253.6	1304.0	1373.5	1418.6	1444.1	1452.9	1444.1
117.5°	736.7	876.8	1012.0	1131.5	1179.5	1227.5	1299.1	1347.1	1373.5	1380.4	1373.5
120°	717.1	843.5	965.0	1068.8	1113.4	1158.0	1226.6	1272.6	1301.0	1310.8	1301.0
122.5°	700.5	817.1	925.8	1022.8	1062.0	1101.2	1160.9	1206.0	1230.5	1238.3	1230.5
125°	684.8	791.6	892.5	978.7	1015.4	1052.2	1109.0	1146.2	1170.7	1178.6	1170.7
127.5°	670.1	766.1	859.2	941.5	975.8	1010.1	1060.0	1095.3	1116.8	1122.7	1116.8
130°	655.4	741.6	825.9	903.3	935.6	967.9	1015.9	1049.2	1068.8	1076.7	1068.8
132.5°	643.7	718.1	794.5	864.1	894.0	923.8	970.9	1004.2	1021.8	1028.7	1021.8
135°	632.9	696.6	761.2	825.9	853.3	880.7	922.9	955.2	972.8	976.7	972.8
137.5°	625.0	678.9	734.8	787.7	812.2	836.7	876.8	905.2	920.9	926.8	920.9
140°	618.2	662.3	709.3	754.4	776.0	797.5	828.8	854.3	869.0	874.9	869.0
142.5°	611.3	648.6	686.8	724.0	741.2	758.3	787.7	810.2	822.9	822.9	822.9
145°	605.4	635.8	668.1	698.5	712.7	726.9	750.4	767.1	776.9	779.8	776.9
147.5°	599.6	626.0	652.5	677.0	687.8	698.5	719.1	732.8	739.7	741.6	739.7
150°	591.7	615.2	636.8	657.4	666.2	675.0	689.7	701.5	707.3	708.3	707.3
152.5°	584.9	604.5	624.1	640.7	648.0	655.4	666.2	676.0	679.9	679.9	679.9
155°	576.1	594.7	610.3	625.0	630.4	635.8	646.6	653.4	657.4	655.4	657.4
157.5°	568.2	582.9	596.6	609.4	613.8	618.2	626.0	631.9	633.9	633.9	633.9
160°	559.4	572.1	582.9	593.7	597.1	600.5	607.4	612.3	613.3	613.3	613.3
162.5°	551.6	561.4	570.2	579.0	581.4	583.9	590.7	593.7	594.7	593.7	594.7
165°	542.7	550.6	557.4	564.3	566.2	568.2	572.1	576.1	576.1	575.1	576.1
167.5°	533.9	539.8	545.7	550.6	552.6	554.5	556.5	558.4	558.4	557.4	558.4
170°	527.1	532.0	534.9	538.8	539.8	540.8	541.8	544.7	543.7	541.8	543.7
172.5°	520.2	523.2	525.1	528.1	528.6	529.0	530.0	531.0	530.0	529.0	530.0
175°	514.3	517.3	518.3	519.2	519.7	520.2	520.2	521.2	520.2	518.3	520.2
177.5°	510.4	512.4	512.4	513.4	513.4	513.4	513.4	513.4	512.4	510.4	512.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P1009922

CATALOG NUMBER: S122RDIP-B290D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	664.9	661.9	661.0	661.9	661.0	661.4	658.4	647.0	650.0	645.2	647.8
5°	702.6	700.0	694.3	693.4	692.5	691.7	687.3	677.2	673.3	666.7	666.2
7.5°	738.6	738.6	734.2	731.1	727.2	724.1	718.4	703.5	697.4	689.5	685.1
10°	774.1	762.7	767.5	764.4	754.8	753.0	742.5	733.7	721.9	714.0	707.0
12.5°	799.5	796.0	791.6	789.0	786.3	780.6	773.6	751.3	745.1	729.4	721.5
15°	798.6	796.4	797.7	797.7	796.9	795.5	789.9	773.6	763.1	747.8	734.2
17.5°	755.7	761.4	767.1	771.0	779.8	783.7	789.0	779.3	772.8	759.6	745.1
20°	680.7	694.7	711.4	714.9	722.8	746.0	756.5	764.9	767.5	763.1	751.3
22.5°	576.4	588.2	628.6	627.7	639.1	666.7	697.4	722.4	742.1	753.0	748.6
25°	451.5	468.1	489.6	505.8	543.1	584.3	622.4	662.3	696.5	726.7	734.2
27.5°	341.5	363.4	380.5	401.9	420.8	469.4	518.5	580.8	620.7	678.1	707.9
30°	276.1	286.2	303.3	313.4	322.6	359.9	415.5	476.9	547.0	613.2	664.5
32.5°	235.8	242.8	255.5	259.9	269.6	294.6	329.6	385.7	458.0	538.3	605.8
35°	211.7	219.2	221.8	225.7	233.6	249.4	273.5	314.3	379.6	458.0	538.7
37.5°	191.1	195.1	202.5	205.1	207.8	219.6	235.8	264.3	307.7	372.1	461.6
40°	176.6	178.8	182.8	185.0	186.7	195.1	209.5	228.8	260.8	309.9	392.3
42.5°	161.3	163.9	166.6	169.2	171.4	178.0	186.7	205.1	226.6	263.9	323.5
45°	146.4	148.2	151.2	153.0	156.0	161.3	169.2	181.9	201.2	224.9	273.1
47.5°	132.8	135.0	136.3	138.5	140.7	146.4	153.9	162.2	178.0	201.2	236.3
50°	120.5	123.2	124.9	125.4	127.1	132.4	138.5	147.7	157.8	175.8	206.4
52.5°	111.8	112.2	113.5	115.3	114.8	117.9	123.6	130.6	141.1	155.6	178.0
55°	101.7	103.0	103.9	104.3	104.3	106.9	110.0	116.6	124.9	136.8	155.6
57.5°	89.0	90.3	92.9	93.8	95.1	96.4	97.7	102.1	109.1	120.5	135.9
60°	75.8	76.7	79.3	81.1	82.0	85.5	87.2	90.7	94.7	103.0	117.5
62.5°	60.9	61.8	63.1	64.9	66.6	71.9	76.3	79.8	82.8	88.5	100.4
65°	53.0	53.5	54.4	54.8	55.2	57.4	61.4	66.2	71.9	76.3	83.3
67.5°	46.0	46.5	46.9	47.8	48.2	48.7	50.4	51.7	57.4	63.6	68.8
70°	39.4	40.3	40.8	40.8	41.2	42.1	43.0	44.7	46.5	49.5	56.1
72.5°	33.3	33.8	34.6	34.6	34.6	35.5	36.4	37.3	38.1	39.9	42.5
75°	27.6	28.5	28.5	28.5	28.9	28.9	29.8	30.7	31.6	32.9	33.8
77.5°	22.8	22.8	22.8	22.8	23.2	23.2	23.7	24.5	25.0	25.4	26.3
80°	17.1	17.5	17.5	17.5	18.0	18.0	18.0	18.8	19.3	19.3	20.2
82.5°	12.7	12.7	12.7	13.1	12.7	13.1	13.1	13.6	13.1	13.6	14.0
85°	7.9	7.9	7.9	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.8
87.5°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	4.4	3.9	3.9
90°	32.3	32.3	32.3	31.8	31.3	29.4	31.3	32.3	33.3	32.3	26.5
92.5°	60.7	64.7	65.6	69.6	73.5	84.3	98.9	126.4	150.9	148.9	115.6
95°	113.6	121.5	134.2	145.0	155.8	196.9	256.7	336.0	384.0	340.0	226.3
97.5°	203.8	223.4	261.6	291.0	320.4	419.3	525.1	630.9	626.0	484.0	300.8
100°	396.8	438.9	520.2	579.5	638.8	773.0	894.5	915.0	774.0	532.9	321.3
102.5°	746.5	825.9	916.0	979.7	1043.4	1132.5	1136.4	1020.8	778.8	514.3	322.3
105°	1159.9	1220.7	1281.4	1297.6	1313.8	1301.0	1190.3	986.5	725.9	488.9	327.2
107.5°	1422.5	1431.3	1432.3	1412.7	1393.1	1297.1	1132.5	914.0	677.0	475.1	338.0
110°	1495.0	1476.4	1434.3	1394.1	1353.9	1228.5	1053.2	846.4	643.7	471.2	351.7

TEST NUMBER: P1009922

CATALOG NUMBER: S122RDIP-B290D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1475.4	1441.1	1378.4	1330.9	1283.4	1147.2	980.7	799.4	622.1	472.2	366.4
115°	1418.6	1373.5	1304.0	1253.6	1203.1	1074.7	923.8	762.2	607.4	476.1	381.1
117.5°	1347.1	1299.1	1227.5	1179.5	1131.5	1012.0	876.8	736.7	599.6	482.0	396.8
120°	1272.6	1226.6	1158.0	1113.4	1068.8	965.0	843.5	717.1	592.7	487.9	412.4
122.5°	1206.0	1160.9	1101.2	1062.0	1022.8	925.8	817.1	700.5	588.8	494.7	426.2
125°	1146.2	1109.0	1052.2	1015.4	978.7	892.5	791.6	684.8	583.9	501.6	440.9
127.5°	1095.3	1060.0	1010.1	975.8	941.5	859.2	766.1	670.1	581.0	508.5	454.6
130°	1049.2	1015.9	967.9	935.6	903.3	825.9	741.6	655.4	579.0	516.3	467.3
132.5°	1004.2	970.9	923.8	894.0	864.1	794.5	718.1	643.7	578.0	524.1	480.0
135°	955.2	922.9	880.7	853.3	825.9	761.2	696.6	632.9	577.0	530.0	490.8
137.5°	905.2	876.8	836.7	812.2	787.7	734.8	678.9	625.0	577.0	535.9	499.6
140°	854.3	828.8	797.5	776.0	754.4	709.3	662.3	618.2	576.1	539.8	506.5
142.5°	810.2	787.7	758.3	741.2	724.0	686.8	648.6	611.3	576.1	542.7	512.4
145°	767.1	750.4	726.9	712.7	698.5	668.1	635.8	605.4	574.1	544.7	517.3
147.5°	732.8	719.1	698.5	687.8	677.0	652.5	626.0	599.6	571.2	545.7	520.2
150°	701.5	689.7	675.0	666.2	657.4	636.8	615.2	591.7	568.2	544.7	522.2
152.5°	676.0	666.2	655.4	648.0	640.7	624.1	604.5	584.9	563.3	542.7	523.2
155°	653.4	646.6	635.8	630.4	625.0	610.3	594.7	576.1	557.4	540.8	524.1
157.5°	631.9	626.0	618.2	613.8	609.4	596.6	582.9	568.2	551.6	536.9	524.1
160°	612.3	607.4	600.5	597.1	593.7	582.9	572.1	559.4	545.7	533.9	524.1
162.5°	593.7	590.7	583.9	581.4	579.0	570.2	561.4	551.6	540.8	531.0	523.2
165°	576.1	572.1	568.2	566.2	564.3	557.4	550.6	542.7	533.9	527.1	521.2
167.5°	558.4	556.5	554.5	552.6	550.6	545.7	539.8	533.9	528.1	523.2	520.2
170°	544.7	541.8	540.8	539.8	538.8	534.9	532.0	527.1	523.2	520.2	518.3
172.5°	531.0	530.0	529.0	528.6	528.1	525.1	523.2	520.2	517.3	516.3	515.3
175°	521.2	520.2	520.2	519.7	519.2	518.3	517.3	514.3	513.4	512.4	513.4
177.5°	513.4	513.4	513.4	513.4	513.4	512.4	512.4	510.4	509.4	510.4	512.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P1009922

CATALOG NUMBER: S122RDIP-B290D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	643.9	641.7	641.7	640.4	640.4	633.4	633.4	635.6	632.9	629.9	625.5
5°	660.5	655.7	654.4	652.7	647.0	638.2	634.7	633.4	628.1	621.5	614.1
7.5°	676.3	668.4	664.5	660.5	653.1	640.8	633.8	629.0	621.1	611.0	601.4
10°	691.7	681.6	671.5	666.7	656.2	640.8	630.7	622.9	611.5	597.9	584.3
12.5°	705.7	684.7	682.9	673.3	657.9	640.4	625.0	613.6	599.2	583.4	567.6
15°	718.0	696.5	686.0	677.2	657.0	635.1	618.9	604.9	585.6	567.6	548.3
17.5°	724.1	700.9	693.9	679.4	658.8	630.3	608.4	591.3	570.3	548.8	526.9
20°	730.2	703.1	691.7	681.6	653.5	621.1	596.6	576.8	553.6	528.2	504.1
22.5°	733.3	703.1	689.5	675.5	648.3	611.0	582.1	558.9	531.7	505.8	476.9
25°	728.0	700.4	684.2	669.8	639.1	598.7	565.4	539.1	510.2	480.8	451.5
27.5°	714.9	694.3	675.5	660.5	626.4	583.0	547.9	518.1	488.3	455.4	425.6
30°	690.4	681.1	666.2	649.6	612.3	568.9	527.3	496.6	463.7	430.9	399.7
32.5°	652.2	660.1	650.5	636.0	595.7	549.7	505.4	474.3	438.3	402.8	374.3
35°	605.8	633.8	628.6	618.5	578.1	529.1	484.8	447.1	411.1	375.2	346.7
37.5°	554.9	597.4	601.8	595.7	558.0	508.0	459.4	422.5	385.7	349.3	320.4
40°	485.2	550.5	564.6	567.2	536.9	482.6	431.7	395.8	359.4	323.9	288.9
42.5°	421.2	503.6	521.2	532.1	510.2	457.6	406.3	366.4	330.5	298.5	263.4
45°	361.2	447.1	475.6	489.6	480.0	429.1	376.1	338.8	305.9	276.6	242.8
47.5°	299.4	385.7	425.6	448.0	448.0	400.2	347.1	310.3	278.8	253.8	224.0
50°	258.2	330.1	371.3	400.6	408.5	370.8	320.8	284.9	255.1	227.9	205.1
52.5°	220.0	284.5	318.7	349.3	372.1	339.3	291.5	259.0	229.7	204.3	186.3
55°	190.2	238.4	269.6	303.3	328.7	307.3	263.0	231.4	206.0	185.0	169.6
57.5°	161.7	203.8	229.2	259.0	286.2	270.0	234.5	207.3	185.0	166.6	153.0
60°	137.6	171.8	191.5	214.8	248.5	237.1	207.8	182.8	164.8	148.2	136.8
62.5°	117.0	144.2	160.9	177.5	208.2	202.9	180.1	160.9	145.5	131.5	121.9
65°	96.0	118.3	131.5	146.0	170.5	172.7	154.3	140.7	126.7	114.4	105.6
67.5°	77.6	95.1	106.9	119.2	138.9	145.1	132.4	121.0	109.1	99.1	91.2
70°	62.7	75.0	83.7	93.4	109.6	117.0	110.5	102.6	92.9	84.6	77.6
72.5°	49.5	57.4	62.7	70.1	83.3	90.7	90.3	83.3	76.3	70.6	64.9
75°	36.4	42.5	46.9	51.7	62.2	69.3	71.0	67.9	60.9	56.5	52.2
77.5°	27.6	31.1	33.3	36.8	44.3	50.4	53.0	52.2	47.3	43.8	40.8
80°	21.0	21.9	22.8	24.1	30.2	35.9	37.7	37.3	34.6	33.3	29.8
82.5°	14.9	15.3	15.8	16.2	18.4	23.2	25.0	25.9	23.7	22.4	19.3
85°	8.8	9.2	9.2	10.1	10.5	11.8	14.9	14.9	14.5	12.7	12.3
87.5°	4.4	4.4	3.9	3.9	4.4	4.8	5.7	6.6	5.7	5.3	4.8
90°	19.6	14.7	13.2	11.8	9.8	7.8	3.9	1.0	3.9	7.8	9.8
92.5°	78.4	51.9	46.5	41.1	33.3	28.4	20.6	14.7	20.6	28.4	33.3
95°	141.1	96.0	84.2	72.5	56.8	48.0	38.2	34.3	38.2	48.0	56.8
97.5°	182.2	124.4	111.2	98.0	80.3	67.6	56.8	50.9	56.8	67.6	80.3
100°	201.8	149.9	136.2	122.5	102.9	87.2	78.4	75.4	78.4	87.2	102.9
102.5°	219.4	172.4	158.7	145.0	124.4	108.7	99.9	98.0	99.9	108.7	124.4
105°	240.0	194.0	180.2	166.5	145.0	130.3	123.4	119.5	123.4	130.3	145.0
107.5°	260.6	215.5	201.8	188.1	166.5	152.8	146.0	143.0	146.0	152.8	166.5
110°	281.2	238.1	223.9	209.7	189.1	176.3	170.5	166.5	170.5	176.3	189.1

TEST NUMBER: P1009922

CATALOG NUMBER: S122RDIP-B290D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	300.8	259.6	244.9	230.2	210.6	198.9	192.0	188.1	192.0	198.9	210.6
115°	321.3	279.2	266.0	252.8	233.2	221.4	215.5	210.6	215.5	221.4	233.2
117.5°	340.0	300.8	287.0	273.3	254.7	243.9	238.1	234.1	238.1	243.9	254.7
120°	359.5	321.3	307.6	293.9	274.3	265.5	259.6	255.7	259.6	265.5	274.3
122.5°	378.2	342.9	328.7	314.5	294.9	285.1	279.2	276.3	279.2	285.1	294.9
125°	396.8	361.5	347.8	334.1	314.5	302.7	296.8	293.9	296.8	302.7	314.5
127.5°	414.4	380.1	365.9	351.7	333.1	320.4	312.5	308.6	312.5	320.4	333.1
130°	430.1	395.8	382.1	368.4	348.8	335.1	325.3	321.3	325.3	335.1	348.8
132.5°	443.8	411.5	397.8	384.0	363.5	348.8	338.0	333.1	338.0	348.8	363.5
135°	456.5	425.2	411.5	397.8	375.2	360.5	348.8	344.8	348.8	360.5	375.2
137.5°	467.3	436.0	423.2	410.5	388.0	372.3	360.5	355.6	360.5	372.3	388.0
140°	476.1	446.7	434.0	421.3	399.7	384.0	372.3	368.4	372.3	384.0	399.7
142.5°	483.0	454.6	442.8	431.1	410.5	394.8	384.0	381.1	384.0	394.8	410.5
145°	489.8	463.4	452.6	441.8	422.2	407.5	397.8	393.8	397.8	407.5	422.2
147.5°	495.7	470.2	460.4	450.7	434.0	420.3	410.5	407.5	410.5	420.3	434.0
150°	499.6	477.1	468.3	459.5	444.8	432.0	424.2	421.3	424.2	432.0	444.8
152.5°	503.6	484.0	476.2	468.3	454.6	443.8	436.0	435.0	436.0	443.8	454.6
155°	507.5	490.8	483.4	476.1	465.4	454.6	448.7	447.7	448.7	454.6	465.4
157.5°	510.4	495.7	489.4	483.0	474.2	464.4	459.5	458.5	459.5	464.4	474.2
160°	512.4	500.6	495.2	489.8	482.0	474.2	470.2	469.3	470.2	474.2	482.0
162.5°	513.4	503.6	499.6	495.7	488.9	483.0	479.1	480.0	479.1	483.0	488.9
165°	514.3	505.5	502.6	499.6	494.7	488.9	486.9	487.9	486.9	488.9	494.7
167.5°	514.3	507.5	505.6	503.6	499.6	495.7	493.8	494.7	493.8	495.7	499.6
170°	513.4	508.5	507.0	505.5	503.6	500.6	499.6	501.6	499.6	500.6	503.6
172.5°	512.4	509.4	508.4	507.5	506.5	503.6	504.5	505.5	504.5	503.6	506.5
175°	511.4	509.4	509.0	508.5	508.5	506.5	507.5	508.5	507.5	506.5	508.5
177.5°	510.4	509.4	509.4	509.4	509.4	507.5	508.5	510.4	508.5	507.5	509.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P1009922

CATALOG NUMBER: S122RDIP-B290D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	623.7	624.2	625.5	621.5	615.4	612.8	604.9	603.6	602.3	602.3	603.6
5°	609.7	607.9	608.4	600.9	592.2	586.9	576.0	577.7	572.0	568.5	569.4
7.5°	594.4	589.5	589.1	579.5	568.5	558.9	547.5	544.8	539.6	533.4	530.8
10°	575.1	571.6	565.0	554.0	540.0	532.1	516.8	507.6	506.3	497.1	493.5
12.5°	555.4	549.2	542.6	527.3	511.5	498.8	487.4	477.3	470.3	462.4	457.2
15°	532.6	525.1	517.7	501.4	483.0	470.3	453.2	438.3	417.7	401.5	392.3
17.5°	507.6	499.2	489.2	471.2	453.2	435.7	404.1	386.6	372.1	362.5	356.8
20°	481.7	472.5	462.4	444.5	413.3	382.7	365.1	351.5	342.8	333.1	326.1
22.5°	454.5	444.9	433.9	405.9	373.0	351.5	337.9	325.2	312.5	307.3	303.8
25°	429.1	420.3	406.3	368.2	342.3	322.6	307.3	298.9	292.4	285.3	278.8
27.5°	402.8	386.6	366.9	334.9	318.7	298.5	287.5	281.4	270.0	265.2	262.1
30°	371.3	353.3	334.4	311.6	292.8	278.8	268.7	258.6	252.0	247.2	242.0
32.5°	339.3	322.2	310.3	286.7	272.6	258.2	248.5	242.4	232.7	229.7	227.5
35°	311.6	297.2	286.7	267.4	254.2	241.1	234.1	224.9	218.7	213.0	209.5
37.5°	284.5	276.6	265.6	249.4	235.4	224.9	215.2	212.1	203.8	200.8	197.2
40°	265.6	253.8	244.6	230.6	218.7	207.3	201.2	194.2	188.5	183.7	182.3
42.5°	242.8	234.1	228.8	213.5	201.2	194.6	187.2	179.3	174.9	170.9	166.1
45°	225.7	217.8	210.4	198.1	187.2	178.8	172.3	167.0	159.5	157.8	150.3
47.5°	207.8	199.9	194.2	181.9	171.8	163.9	159.1	152.1	146.0	142.0	138.5
50°	189.8	183.2	178.0	167.4	158.7	150.3	143.8	136.8	134.1	127.6	125.4
52.5°	172.7	168.3	162.6	152.5	143.8	136.8	129.7	124.0	120.1	116.6	114.0
55°	158.2	151.2	148.6	137.6	130.2	122.7	116.6	113.1	108.3	106.1	103.9
57.5°	142.0	138.1	133.7	125.4	117.0	110.0	105.6	100.4	97.7	95.1	93.4
60°	128.0	122.3	118.8	111.8	104.3	97.7	93.8	89.9	86.3	84.2	80.7
62.5°	111.8	107.4	105.2	97.7	91.6	85.5	82.0	78.0	75.4	71.4	67.1
65°	97.7	94.2	91.6	85.5	79.8	74.1	70.6	65.7	62.2	60.0	59.6
67.5°	85.5	82.8	78.9	73.2	67.5	63.1	59.2	55.2	54.8	53.9	53.9
70°	71.9	69.3	67.1	60.9	56.1	51.3	50.4	49.1	47.8	47.3	46.5
72.5°	60.0	57.9	55.2	50.0	45.1	43.8	43.0	42.1	40.8	40.3	39.9
75°	48.7	45.6	43.8	39.0	37.7	36.8	35.9	34.6	33.8	33.3	32.4
77.5°	37.3	34.2	34.2	31.6	30.7	29.4	28.5	27.6	27.2	26.3	26.3
80°	26.3	26.3	25.4	24.1	22.8	22.4	21.0	20.6	20.2	20.6	19.7
82.5°	19.3	17.5	17.5	16.7	15.8	15.3	14.5	14.5	14.0	14.0	14.0
85°	11.0	11.0	10.5	9.6	9.2	9.2	8.8	8.8	8.3	8.3	7.9
87.5°	4.4	3.9	4.4	3.9	3.9	3.5	3.5	3.5	3.1	3.5	3.1
90°	11.8	13.2	14.7	19.6	26.5	32.3	33.3	32.3	31.3	29.4	31.3
92.5°	41.1	46.5	51.9	78.4	115.6	148.9	150.9	126.4	98.9	84.3	73.5
95°	72.5	84.2	96.0	141.1	226.3	340.0	384.0	336.0	256.7	196.9	155.8
97.5°	98.0	111.2	124.4	182.2	300.8	484.0	626.0	630.9	525.1	419.3	320.4
100°	122.5	136.2	149.9	201.8	321.3	532.9	774.0	915.0	894.5	773.0	638.8
102.5°	145.0	158.7	172.4	219.4	322.3	514.3	778.8	1020.8	1136.4	1132.5	1043.4
105°	166.5	180.2	194.0	240.0	327.2	488.9	725.9	986.5	1190.3	1301.0	1313.8
107.5°	188.1	201.8	215.5	260.6	338.0	475.1	677.0	914.0	1132.5	1297.1	1393.1
110°	209.7	223.9	238.1	281.2	351.7	471.2	643.7	846.4	1053.2	1228.5	1353.9

TEST NUMBER: P1009922

CATALOG NUMBER: S122RDIP-B290D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	230.2	244.9	259.6	300.8	366.4	472.2	622.1	799.4	980.7	1147.2	1283.4
115°	252.8	266.0	279.2	321.3	381.1	476.1	607.4	762.2	923.8	1074.7	1203.1
117.5°	273.3	287.0	300.8	340.0	396.8	482.0	599.6	736.7	876.8	1012.0	1131.5
120°	293.9	307.6	321.3	359.5	412.4	487.9	592.7	717.1	843.5	965.0	1068.8
122.5°	314.5	328.7	342.9	378.2	426.2	494.7	588.8	700.5	817.1	925.8	1022.8
125°	334.1	347.8	361.5	396.8	440.9	501.6	583.9	684.8	791.6	892.5	978.7
127.5°	351.7	365.9	380.1	414.4	454.6	508.5	581.0	670.1	766.1	859.2	941.5
130°	368.4	382.1	395.8	430.1	467.3	516.3	579.0	655.4	741.6	825.9	903.3
132.5°	384.0	397.8	411.5	443.8	480.0	524.1	578.0	643.7	718.1	794.5	864.1
135°	397.8	411.5	425.2	456.5	490.8	530.0	577.0	632.9	696.6	761.2	825.9
137.5°	410.5	423.2	436.0	467.3	499.6	535.9	577.0	625.0	678.9	734.8	787.7
140°	421.3	434.0	446.7	476.1	506.5	539.8	576.1	618.2	662.3	709.3	754.4
142.5°	431.1	442.8	454.6	483.0	512.4	542.7	576.1	611.3	648.6	686.8	724.0
145°	441.8	452.6	463.4	489.8	517.3	544.7	574.1	605.4	635.8	668.1	698.5
147.5°	450.7	460.4	470.2	495.7	520.2	545.7	571.2	599.6	626.0	652.5	677.0
150°	459.5	468.3	477.1	499.6	522.2	544.7	568.2	591.7	615.2	636.8	657.4
152.5°	468.3	476.2	484.0	503.6	523.2	542.7	563.3	584.9	604.5	624.1	640.7
155°	476.1	483.4	490.8	507.5	524.1	540.8	557.4	576.1	594.7	610.3	625.0
157.5°	483.0	489.4	495.7	510.4	524.1	536.9	551.6	568.2	582.9	596.6	609.4
160°	489.8	495.2	500.6	512.4	524.1	533.9	545.7	559.4	572.1	582.9	593.7
162.5°	495.7	499.6	503.6	513.4	523.2	531.0	540.8	551.6	561.4	570.2	579.0
165°	499.6	502.6	505.5	514.3	521.2	527.1	533.9	542.7	550.6	557.4	564.3
167.5°	503.6	505.6	507.5	514.3	520.2	523.2	528.1	533.9	539.8	545.7	550.6
170°	505.5	507.0	508.5	513.4	518.3	520.2	523.2	527.1	532.0	534.9	538.8
172.5°	507.5	508.4	509.4	512.4	515.3	516.3	517.3	520.2	523.2	525.1	528.1
175°	508.5	509.0	509.4	511.4	513.4	512.4	513.4	514.3	517.3	518.3	519.2
177.5°	509.4	509.4	509.4	510.4	512.4	510.4	509.4	510.4	512.4	512.4	513.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P1009922

CATALOG NUMBER: S122RDIP-B290D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	603.6	602.7	600.1	600.9	599.6	599.6	598.7	598.7	598.7	600.9	599.6
5°	570.7	567.6	564.6	563.2	561.9	560.6	560.6	560.2	564.1	563.2	566.7
7.5°	529.9	529.1	522.9	522.9	520.7	519.8	522.0	522.5	522.9	523.8	526.0
10°	493.5	491.4	482.6	483.5	482.2	480.4	481.7	480.8	483.9	484.8	483.9
12.5°	450.6	446.6	437.0	432.2	426.9	423.0	427.8	424.3	436.6	440.1	449.7
15°	393.6	386.2	379.6	379.6	374.8	371.3	373.4	377.4	380.0	384.0	385.7
17.5°	355.5	352.4	347.1	344.1	342.8	341.5	341.5	343.2	348.9	348.5	352.0
20°	323.0	321.3	318.7	314.7	313.4	312.5	312.5	312.5	316.5	320.0	322.2
22.5°	300.7	299.4	297.6	292.4	289.7	288.9	291.0	292.4	295.4	298.1	300.2
25°	278.3	275.3	272.2	270.4	269.1	269.1	270.0	270.4	271.8	273.1	275.7
27.5°	259.9	257.7	253.3	248.5	248.5	247.2	248.1	249.0	252.0	256.4	258.6
30°	239.3	238.9	237.1	235.4	233.6	232.7	234.5	235.8	236.3	238.4	238.4
32.5°	224.4	221.4	218.3	216.5	215.7	215.2	215.7	217.4	217.4	220.0	223.1
35°	209.5	207.8	204.7	201.6	200.8	198.6	200.3	202.1	205.1	206.4	207.8
37.5°	193.3	191.1	189.8	188.9	187.2	187.6	186.3	188.9	191.5	191.1	192.0
40°	181.0	177.1	173.1	172.7	172.3	171.8	171.8	172.3	174.0	175.8	178.4
42.5°	165.2	163.9	160.4	156.9	156.0	155.2	154.3	156.0	159.5	162.6	163.9
45°	149.0	147.3	146.4	143.8	142.0	141.6	140.7	142.9	146.0	147.3	148.2
47.5°	134.1	133.7	131.1	131.5	130.2	130.6	130.2	131.5	131.5	132.8	133.7
50°	124.0	122.7	121.4	120.5	119.2	119.2	118.8	119.2	121.0	122.7	122.3
52.5°	114.0	111.8	111.3	110.9	110.0	110.9	109.6	110.0	111.8	112.6	112.2
55°	102.1	101.7	100.8	99.9	99.5	99.1	99.1	99.1	100.8	102.1	102.6
57.5°	92.9	90.7	89.0	89.0	87.2	86.8	87.7	88.1	89.4	90.3	91.2
60°	80.2	79.3	76.7	75.4	72.8	72.3	72.3	74.1	76.3	79.3	80.2
62.5°	66.6	65.3	64.9	64.9	64.9	64.9	64.9	64.9	64.9	65.3	65.3
65°	59.2	59.6	59.2	58.7	59.2	59.2	58.7	58.7	58.7	59.2	59.6
67.5°	53.0	52.6	53.0	52.6	52.2	52.2	51.7	52.2	52.6	53.0	53.0
70°	46.0	46.0	45.6	46.0	45.6	45.1	44.7	44.7	45.6	46.0	46.0
72.5°	39.4	39.4	39.0	39.0	38.1	38.1	38.6	38.1	38.1	39.4	39.4
75°	32.9	32.4	32.0	32.0	31.6	31.6	31.6	31.1	32.0	32.0	32.4
77.5°	25.9	25.9	25.9	25.4	25.4	25.0	25.0	25.4	25.4	25.4	25.9
80°	19.7	19.7	19.7	19.3	18.8	18.8	18.8	18.8	18.8	19.3	18.8
82.5°	13.6	13.6	13.6	13.6	13.6	13.1	13.1	13.1	13.6	13.6	13.1
85°	8.3	7.9	8.3	8.3	7.9	8.3	7.9	7.9	7.5	7.5	7.9
87.5°	3.5	3.1	2.6	2.6	3.1	2.6	2.6	2.6	3.1	2.6	2.6
90°	31.8	32.3	32.3	32.3	32.3	32.3	32.3	32.3	32.3	32.3	31.8
92.5°	69.6	65.6	64.7	60.7	61.7	59.8	61.7	60.7	64.7	65.6	69.6
95°	145.0	134.2	121.5	113.6	110.7	111.7	110.7	113.6	121.5	134.2	145.0
97.5°	291.0	261.6	223.4	203.8	193.0	187.1	193.0	203.8	223.4	261.6	291.0
100°	579.5	520.2	438.9	396.8	368.4	350.7	368.4	396.8	438.9	520.2	579.5
102.5°	979.7	916.0	825.9	746.5	709.3	683.8	709.3	746.5	825.9	916.0	979.7
105°	1297.6	1281.4	1220.7	1159.9	1117.8	1104.1	1117.8	1159.9	1220.7	1281.4	1297.6
107.5°	1412.7	1432.3	1431.3	1422.5	1409.8	1387.2	1409.8	1422.5	1431.3	1432.3	1412.7
110°	1394.1	1434.3	1476.4	1495.0	1503.8	1502.8	1503.8	1495.0	1476.4	1434.3	1394.1

TEST NUMBER: P1009922

CATALOG NUMBER: S122RDIP-B290D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1330.9	1378.4	1441.1	1475.4	1494.0	1500.9	1494.0	1475.4	1441.1	1378.4	1330.9
115°	1253.6	1304.0	1373.5	1418.6	1444.1	1452.9	1444.1	1418.6	1373.5	1304.0	1253.6
117.5°	1179.5	1227.5	1299.1	1347.1	1373.5	1380.4	1373.5	1347.1	1299.1	1227.5	1179.5
120°	1113.4	1158.0	1226.6	1272.6	1301.0	1310.8	1301.0	1272.6	1226.6	1158.0	1113.4
122.5°	1062.0	1101.2	1160.9	1206.0	1230.5	1238.3	1230.5	1206.0	1160.9	1101.2	1062.0
125°	1015.4	1052.2	1109.0	1146.2	1170.7	1178.6	1170.7	1146.2	1109.0	1052.2	1015.4
127.5°	975.8	1010.1	1060.0	1095.3	1116.8	1122.7	1116.8	1095.3	1060.0	1010.1	975.8
130°	935.6	967.9	1015.9	1049.2	1068.8	1076.7	1068.8	1049.2	1015.9	967.9	935.6
132.5°	894.0	923.8	970.9	1004.2	1021.8	1028.7	1021.8	1004.2	970.9	923.8	894.0
135°	853.3	880.7	922.9	955.2	972.8	976.7	972.8	955.2	922.9	880.7	853.3
137.5°	812.2	836.7	876.8	905.2	920.9	926.8	920.9	905.2	876.8	836.7	812.2
140°	776.0	797.5	828.8	854.3	869.0	874.9	869.0	854.3	828.8	797.5	776.0
142.5°	741.2	758.3	787.7	810.2	822.9	822.9	822.9	810.2	787.7	758.3	741.2
145°	712.7	726.9	750.4	767.1	776.9	779.8	776.9	767.1	750.4	726.9	712.7
147.5°	687.8	698.5	719.1	732.8	739.7	741.6	739.7	732.8	719.1	698.5	687.8
150°	666.2	675.0	689.7	701.5	707.3	708.3	707.3	701.5	689.7	675.0	666.2
152.5°	648.0	655.4	666.2	676.0	679.9	679.9	679.9	676.0	666.2	655.4	648.0
155°	630.4	635.8	646.6	653.4	657.4	655.4	657.4	653.4	646.6	635.8	630.4
157.5°	613.8	618.2	626.0	631.9	633.9	633.9	633.9	631.9	626.0	618.2	613.8
160°	597.1	600.5	607.4	612.3	613.3	613.3	613.3	612.3	607.4	600.5	597.1
162.5°	581.4	583.9	590.7	593.7	594.7	593.7	594.7	593.7	590.7	583.9	581.4
165°	566.2	568.2	572.1	576.1	576.1	575.1	576.1	576.1	572.1	568.2	566.2
167.5°	552.6	554.5	556.5	558.4	558.4	557.4	558.4	558.4	556.5	554.5	552.6
170°	539.8	540.8	541.8	544.7	543.7	541.8	543.7	544.7	541.8	540.8	539.8
172.5°	528.6	529.0	530.0	531.0	530.0	529.0	530.0	531.0	530.0	529.0	528.6
175°	519.7	520.2	520.2	521.2	520.2	518.3	520.2	521.2	520.2	520.2	519.7
177.5°	513.4	513.4	513.4	513.4	512.4	510.4	512.4	513.4	513.4	513.4	513.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P1009922

CATALOG NUMBER: S122RDIP-B290D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	600.9	603.1	602.3	597.4	602.3	603.6	606.2	608.8	610.6	613.2	615.4
5°	563.2	567.6	570.3	567.6	576.4	577.7	583.8	587.3	592.6	597.0	600.5
7.5°	527.7	531.2	536.5	537.4	542.6	548.8	557.5	566.3	574.6	579.0	583.0
10°	489.6	495.7	503.6	501.9	509.8	519.4	528.6	542.6	549.7	557.5	564.6
12.5°	451.5	455.4	465.9	469.4	480.8	488.3	501.0	509.8	527.3	536.5	542.6
15°	384.8	401.1	414.2	430.0	444.9	458.9	470.3	486.1	501.4	508.5	518.5
17.5°	354.6	362.1	369.9	377.8	397.1	422.1	442.3	459.4	472.5	481.7	493.5
20°	323.0	330.5	339.3	346.7	358.5	376.5	401.5	430.9	446.6	456.3	467.7
22.5°	300.7	307.7	313.4	320.0	329.2	342.3	361.2	397.6	418.6	430.4	440.5
25°	276.6	285.3	291.5	296.3	303.8	318.2	333.6	354.2	391.9	401.1	415.1
27.5°	259.9	262.6	269.6	277.0	284.5	292.4	308.1	325.7	351.1	371.3	388.4
30°	240.2	246.8	253.3	256.4	263.0	274.4	284.0	302.9	322.6	338.4	359.0
32.5°	225.3	229.2	233.6	241.1	247.2	255.1	264.7	280.5	297.2	307.3	323.0
35°	208.6	211.3	220.5	223.5	229.7	237.6	247.2	259.5	277.5	285.3	296.7
37.5°	192.9	199.0	201.6	208.6	214.3	222.2	229.2	243.3	255.1	264.3	274.8
40°	180.6	183.2	188.0	194.2	199.0	205.1	213.9	224.0	236.7	244.1	253.3
42.5°	165.7	167.9	174.0	177.5	185.4	191.1	196.4	208.6	220.0	225.7	234.9
45°	149.5	154.7	158.7	165.7	170.1	177.1	183.7	192.4	202.9	209.5	214.8
47.5°	135.4	140.7	144.6	151.2	158.2	161.3	168.3	177.5	187.2	192.4	199.9
50°	124.0	125.8	133.2	136.3	143.8	149.9	154.7	162.6	173.1	176.2	182.3
52.5°	113.1	114.4	119.2	123.2	129.7	135.0	141.1	148.6	157.4	162.2	167.0
55°	103.4	104.3	106.5	110.9	115.3	121.9	127.6	134.6	142.0	147.3	151.7
57.5°	92.5	94.2	96.0	98.6	103.0	109.1	115.3	121.9	128.0	131.5	137.2
60°	79.8	82.4	85.5	88.5	91.6	96.0	103.0	109.1	114.8	117.9	122.3
62.5°	66.2	71.4	74.1	77.6	80.2	84.2	89.4	96.4	100.4	104.3	107.8
65°	59.6	60.0	60.5	64.0	68.8	72.8	77.6	82.8	89.0	91.6	94.2
67.5°	53.0	53.5	54.4	54.8	56.5	60.9	66.2	71.9	76.7	78.5	81.1
70°	46.5	46.5	48.2	48.7	49.1	49.5	53.9	59.6	64.0	66.2	69.3
72.5°	39.4	39.9	40.8	41.2	42.1	43.0	44.3	47.3	52.6	54.8	58.3
75°	32.4	32.9	33.3	33.8	35.1	35.5	36.8	38.6	40.8	43.4	45.6
77.5°	25.9	25.9	26.3	27.2	28.1	28.5	29.8	30.7	31.6	32.9	34.6
80°	19.3	19.7	19.7	20.6	20.6	21.0	21.5	22.8	23.7	24.5	25.4
82.5°	13.1	14.0	14.0	14.0	14.5	14.9	15.3	15.3	16.2	16.7	18.0
85°	7.9	8.3	8.3	8.3	7.9	8.8	8.8	9.2	9.2	9.2	9.6
87.5°	3.1	2.6	3.1	3.1	3.1	3.5	3.1	3.1	3.5	3.9	3.9
90°	31.3	29.4	31.3	32.3	33.3	32.3	26.5	19.6	14.7	13.2	11.8
92.5°	73.5	84.3	98.9	126.4	150.9	148.9	115.6	78.4	51.9	46.5	41.1
95°	155.8	196.9	256.7	336.0	384.0	340.0	226.3	141.1	96.0	84.2	72.5
97.5°	320.4	419.3	525.1	630.9	626.0	484.0	300.8	182.2	124.4	111.2	98.0
100°	638.8	773.0	894.5	915.0	774.0	532.9	321.3	201.8	149.9	136.2	122.5
102.5°	1043.4	1132.5	1136.4	1020.8	778.8	514.3	322.3	219.4	172.4	158.7	145.0
105°	1313.8	1301.0	1190.3	986.5	725.9	488.9	327.2	240.0	194.0	180.2	166.5
107.5°	1393.1	1297.1	1132.5	914.0	677.0	475.1	338.0	260.6	215.5	201.8	188.1
110°	1353.9	1228.5	1053.2	846.4	643.7	471.2	351.7	281.2	238.1	223.9	209.7

TEST NUMBER: P1009922

CATALOG NUMBER: S122RDIP-B290D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1283.4	1147.2	980.7	799.4	622.1	472.2	366.4	300.8	259.6	244.9	230.2
115°	1203.1	1074.7	923.8	762.2	607.4	476.1	381.1	321.3	279.2	266.0	252.8
117.5°	1131.5	1012.0	876.8	736.7	599.6	482.0	396.8	340.0	300.8	287.0	273.3
120°	1068.8	965.0	843.5	717.1	592.7	487.9	412.4	359.5	321.3	307.6	293.9
122.5°	1022.8	925.8	817.1	700.5	588.8	494.7	426.2	378.2	342.9	328.7	314.5
125°	978.7	892.5	791.6	684.8	583.9	501.6	440.9	396.8	361.5	347.8	334.1
127.5°	941.5	859.2	766.1	670.1	581.0	508.5	454.6	414.4	380.1	365.9	351.7
130°	903.3	825.9	741.6	655.4	579.0	516.3	467.3	430.1	395.8	382.1	368.4
132.5°	864.1	794.5	718.1	643.7	578.0	524.1	480.0	443.8	411.5	397.8	384.0
135°	825.9	761.2	696.6	632.9	577.0	530.0	490.8	456.5	425.2	411.5	397.8
137.5°	787.7	734.8	678.9	625.0	577.0	535.9	499.6	467.3	436.0	423.2	410.5
140°	754.4	709.3	662.3	618.2	576.1	539.8	506.5	476.1	446.7	434.0	421.3
142.5°	724.0	686.8	648.6	611.3	576.1	542.7	512.4	483.0	454.6	442.8	431.1
145°	698.5	668.1	635.8	605.4	574.1	544.7	517.3	489.8	463.4	452.6	441.8
147.5°	677.0	652.5	626.0	599.6	571.2	545.7	520.2	495.7	470.2	460.4	450.7
150°	657.4	636.8	615.2	591.7	568.2	544.7	522.2	499.6	477.1	468.3	459.5
152.5°	640.7	624.1	604.5	584.9	563.3	542.7	523.2	503.6	484.0	476.2	468.3
155°	625.0	610.3	594.7	576.1	557.4	540.8	524.1	507.5	490.8	483.4	476.1
157.5°	609.4	596.6	582.9	568.2	551.6	536.9	524.1	510.4	495.7	489.4	483.0
160°	593.7	582.9	572.1	559.4	545.7	533.9	524.1	512.4	500.6	495.2	489.8
162.5°	579.0	570.2	561.4	551.6	540.8	531.0	523.2	513.4	503.6	499.6	495.7
165°	564.3	557.4	550.6	542.7	533.9	527.1	521.2	514.3	505.5	502.6	499.6
167.5°	550.6	545.7	539.8	533.9	528.1	523.2	520.2	514.3	507.5	505.6	503.6
170°	538.8	534.9	532.0	527.1	523.2	520.2	518.3	513.4	508.5	507.0	505.5
172.5°	528.1	525.1	523.2	520.2	517.3	516.3	515.3	512.4	509.4	508.4	507.5
175°	519.2	518.3	517.3	514.3	513.4	512.4	513.4	511.4	509.4	509.0	508.5
177.5°	513.4	512.4	512.4	510.4	509.4	510.4	512.4	510.4	509.4	509.4	509.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P1009922

CATALOG NUMBER: S122RDIP-B290D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	630.7	630.7	630.7	630.7
2.5°	619.3	618.0	625.9	634.7
5°	606.6	608.8	618.9	631.2
7.5°	593.5	598.3	610.1	626.4
10°	575.1	583.8	601.8	618.5
12.5°	557.1	568.9	586.0	605.8
15°	536.9	550.1	571.1	594.8
17.5°	514.6	529.5	554.0	579.9
20°	490.9	510.6	536.5	564.6
22.5°	464.6	488.3	515.0	546.1
25°	439.2	465.1	491.8	527.7
27.5°	414.2	439.6	469.4	505.8
30°	389.2	412.5	444.5	483.5
32.5°	362.5	386.6	420.3	460.2
35°	337.9	362.1	393.6	433.1
37.5°	311.6	337.5	367.8	408.5
40°	281.0	311.2	340.6	379.6
42.5°	255.5	287.5	316.0	352.8
45°	235.4	265.6	289.3	325.2
47.5°	216.5	241.1	265.2	298.5
50°	198.6	217.4	242.4	272.2
52.5°	180.1	196.4	217.8	245.9
55°	163.5	178.8	198.1	219.6
57.5°	148.2	159.1	178.4	197.7
60°	131.1	142.5	157.4	173.6
62.5°	116.6	125.4	139.4	153.0
65°	101.3	109.6	120.1	132.8
67.5°	87.2	94.7	103.0	113.1
70°	74.5	80.2	86.3	95.1
72.5°	60.9	67.1	72.8	79.8
75°	50.0	52.6	57.4	62.2
77.5°	38.6	42.1	44.7	48.7
80°	27.6	30.7	31.6	34.6
82.5°	18.4	20.2	21.9	22.8
85°	10.5	11.4	13.1	13.6
87.5°	3.9	4.4	5.3	6.1
90°	9.8	7.8	3.9	1.0
92.5°	33.3	28.4	20.6	14.7
95°	56.8	48.0	38.2	34.3
97.5°	80.3	67.6	56.8	50.9
100°	102.9	87.2	78.4	75.4
102.5°	124.4	108.7	99.9	98.0
105°	145.0	130.3	123.4	119.5
107.5°	166.5	152.8	146.0	143.0
110°	189.1	176.3	170.5	166.5

TEST NUMBER: P1009922

CATALOG NUMBER: S122RDIP-B290D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	210.6	198.9	192.0	188.1
115°	233.2	221.4	215.5	210.6
117.5°	254.7	243.9	238.1	234.1
120°	274.3	265.5	259.6	255.7
122.5°	294.9	285.1	279.2	276.3
125°	314.5	302.7	296.8	293.9
127.5°	333.1	320.4	312.5	308.6
130°	348.8	335.1	325.3	321.3
132.5°	363.5	348.8	338.0	333.1
135°	375.2	360.5	348.8	344.8
137.5°	388.0	372.3	360.5	355.6
140°	399.7	384.0	372.3	368.4
142.5°	410.5	394.8	384.0	381.1
145°	422.2	407.5	397.8	393.8
147.5°	434.0	420.3	410.5	407.5
150°	444.8	432.0	424.2	421.3
152.5°	454.6	443.8	436.0	435.0
155°	465.4	454.6	448.7	447.7
157.5°	474.2	464.4	459.5	458.5
160°	482.0	474.2	470.2	469.3
162.5°	488.9	483.0	479.1	480.0
165°	494.7	488.9	486.9	487.9
167.5°	499.6	495.7	493.8	494.7
170°	503.6	500.6	499.6	501.6
172.5°	506.5	503.6	504.5	505.5
175°	508.5	506.5	507.5	508.5
177.5°	509.4	507.5	508.5	510.4
180°	509.4	509.4	509.4	509.4

(END OF REPORT)