

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009928

Luminaire Tested: S122RDIP-B290D925UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009928
REPORT IS A COMBINATION OF REPORTS P988196 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B290D925UB30-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4681.0 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009928

CATALOG NUMBER: S122RDIP-B290D925UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1009928

CATALOG NUMBER: S122RDIP-B290D925UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32
1	92	88	85	81	82	79	76	73	60	59	57	44	43	42	29	28	27
2	84	77	72	67	75	69	64	60	53	50	48	39	37	35	26	25	24
3	77	68	62	56	68	61	55	51	47	44	40	35	32	30	23	22	21
4	71	61	53	48	63	54	48	43	42	38	35	31	28	26	21	19	18
5	65	54	47	41	58	48	42	37	38	33	30	28	25	23	19	17	16
6	60	48	41	36	53	44	37	32	34	30	26	26	23	20	17	16	14
7	55	44	36	31	49	39	33	28	31	27	23	23	20	18	16	14	13
8	51	40	32	27	46	36	30	25	28	24	21	21	18	16	15	13	12
9	48	36	29	24	42	33	27	22	26	22	18	20	17	15	14	12	11
10	44	33	26	22	40	30	24	20	24	20	17	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10075	10075	10075	10075
5°	10100	10702	10135	8550
10°	9987	11313	10059	7060
15°	9772	11315	9936	5304
20°	9510	9353	9717	4376
25°	9195	5844	9394	3723
30°	8791	3743	9031	3205
35°	8299	2876	8569	2743
40°	7754	2417	8083	2399
45°	7168	2058	7467	2014
50°	6569	1749	6875	1742
55°	5905	1519	6225	1500
60°	5316	1159	5599	1145
65°	4764	871	5048	989
70°	4157	697	4482	807
75°	3513	534	3838	609
80°	2786	364	3002	399
85°	1935	188	2119	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 9218 cd/sqm

TEST NUMBER: P1009928

CATALOG NUMBER: S122RDIP-B290D925UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.4	1.3
10°-20°	168.5	3.6
20°-30°	216.9	4.6
30°-40°	205.8	4.4
40°-50°	176.3	3.8
50°-60°	134.3	2.9
60°-70°	84.7	1.8
70°-80°	42.3	0.9
80°-90°	14.2	0.3
90°-100°	200.3	4.3
100°-110°	705.3	15.1
110°-120°	740.7	15.8
120°-130°	609.4	13.0
130°-140°	489.5	10.5
140°-150°	369.8	7.9
150°-160°	260.0	5.6
160°-170°	153.0	3.3
170°-180°	49.8	1.1
0°-30°	445.8	9.5
0°-40°	651.5	13.9
0°-60°	962.2	20.6
0°-90°	1103.3	23.6
90°-120°	1646.3	35.2
90°-150°	3115.0	66.5
90°-180°	3578.0	76.4
0°-180°	4681.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	636	636	636	636	636	
5°	637	708	639	566	637	60
15°	600	799	610	375	600	169
25°	533	426	544	272	533	245
35°	437	210	451	200	437	273
45°	328	146	342	143	328	253
55°	222	101	234	100	222	200
65°	134	53	142	60	134	133
75°	63	28	69	32	63	68
85°	14	8	15	8	14	16
90°	1	33	1	33	1	3
95°	35	113	35	113	35	36
105°	120	1113	120	1113	120	128
115°	212	1465	212	1465	212	211
125°	296	1188	296	1188	296	263
135°	348	985	348	985	348	269
145°	397	786	397	786	397	249
155°	452	661	452	661	452	208
165°	492	580	492	580	492	139
175°	513	523	513	523	513	49
180°	514	514	514	514	514	

TEST NUMBER: P1009928

CATALOG NUMBER: S122RDIP-B290D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5
2.5°	640.5	643.2	644.5	646.3	650.2	652.9	656.9	657.8	657.3	659.1	654.2
5°	637.0	642.7	648.0	652.5	659.5	664.0	668.8	674.6	675.9	682.5	678.6
7.5°	632.1	640.5	648.0	656.9	667.5	673.2	680.8	689.6	693.6	701.6	703.8
10°	624.1	636.1	648.9	658.2	672.8	683.0	690.1	704.2	713.5	725.4	723.7
12.5°	611.3	626.8	644.0	659.5	678.6	685.2	698.5	713.1	725.0	736.1	745.8
15°	600.3	618.0	637.0	656.0	677.7	690.1	703.3	722.3	735.2	754.6	763.0
17.5°	585.2	607.8	630.3	651.6	677.2	691.4	707.7	726.3	745.3	763.9	770.6
20°	569.7	594.1	618.4	647.1	676.3	690.1	706.9	729.9	748.4	763.0	763.0
22.5°	551.2	580.8	608.7	636.1	667.9	687.8	705.1	732.1	745.3	748.4	736.5
25°	532.6	562.2	592.7	626.8	663.1	680.8	700.2	725.4	729.9	717.5	686.5
27.5°	510.5	543.6	578.1	614.9	652.9	675.0	692.7	709.5	701.1	667.9	619.7
30°	487.9	523.7	562.7	597.6	643.6	664.0	679.0	683.9	657.3	603.4	541.0
32.5°	464.5	499.4	540.5	582.6	629.0	648.5	658.2	645.4	596.7	528.6	452.5
35°	437.0	476.4	519.3	563.1	609.1	623.7	629.5	598.0	535.7	447.6	372.0
37.5°	412.3	451.6	497.6	542.3	587.0	594.9	589.2	540.1	460.9	373.8	299.9
40°	383.1	425.1	470.2	520.2	556.9	559.1	545.0	481.3	383.1	301.2	255.7
42.5°	356.1	398.5	443.7	494.5	522.4	514.9	495.9	412.3	319.8	259.7	222.9
45°	328.2	368.5	417.1	462.2	482.2	464.5	435.7	346.8	268.5	223.4	195.1
47.5°	301.2	338.8	387.0	430.4	433.9	414.0	380.0	290.6	232.7	196.4	173.4
50°	274.7	312.3	357.4	393.2	389.7	362.3	323.8	252.6	202.1	173.4	154.4
52.5°	248.2	282.2	326.0	354.3	339.3	312.7	274.7	214.1	176.5	151.3	136.7
55°	221.6	253.5	291.1	314.5	290.6	260.1	233.1	183.6	153.0	132.7	121.6
57.5°	199.5	224.7	259.2	273.4	244.6	220.7	197.3	157.9	132.7	118.1	105.3
60°	175.2	198.2	226.5	234.9	205.2	185.8	165.9	133.6	113.7	100.9	92.4
62.5°	154.4	173.4	195.1	195.1	169.0	154.4	139.3	111.9	95.5	85.4	81.4
65°	134.0	147.7	163.2	161.5	139.3	126.5	114.6	92.4	80.1	73.0	69.0
67.5°	114.1	124.7	134.9	128.7	112.8	101.7	90.7	74.8	66.4	61.5	56.2
70°	96.0	104.4	109.7	104.0	88.0	78.7	70.8	60.2	53.5	47.3	44.2
72.5°	80.5	84.0	85.8	78.7	65.5	60.2	54.4	46.9	41.1	38.0	37.2
75°	62.8	65.9	64.6	59.3	48.2	44.2	39.8	34.5	33.2	31.4	30.5
77.5°	49.1	49.1	46.9	42.0	34.5	31.4	29.6	27.0	25.7	25.2	24.3
80°	34.9	34.5	33.2	27.9	23.4	21.7	21.7	19.9	19.5	18.6	18.6
82.5°	23.0	23.0	21.2	16.8	15.5	15.0	14.6	13.7	13.7	13.3	13.3
85°	13.7	12.8	10.6	9.3	8.8	8.8	8.4	8.0	8.4	8.0	8.0
87.5°	6.2	4.9	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
90°	1.0	4.0	7.9	9.9	11.9	13.4	14.8	19.8	26.7	32.6	33.6
92.5°	14.8	20.7	28.7	33.6	41.5	47.0	52.4	79.0	116.6	150.2	152.1
95°	34.6	38.5	48.4	57.3	73.1	84.9	96.8	142.3	228.2	342.8	387.3
97.5°	51.4	57.3	68.2	81.0	98.8	112.2	125.5	183.8	303.3	488.1	631.3
100°	76.1	79.0	87.9	103.7	123.5	137.4	151.2	203.5	324.1	537.5	780.5
102.5°	98.8	100.8	109.7	125.5	146.2	160.0	173.9	221.3	325.0	518.7	785.4
105°	120.5	124.5	131.4	146.2	168.0	181.8	195.6	242.1	330.0	493.0	732.1
107.5°	144.2	147.2	154.1	168.0	189.7	203.6	217.4	262.8	340.8	479.2	682.7
110°	168.0	171.9	177.8	190.7	211.4	225.8	240.1	283.5	354.7	475.2	649.1



TEST NUMBER: P1009928

CATALOG NUMBER: S122RDIP-B290D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	189.7	193.6	200.6	212.4	232.2	247.0	261.8	303.3	369.5	476.2	627.4
115°	212.4	217.4	223.3	235.1	254.9	268.2	281.6	324.1	384.3	480.1	612.5
117.5°	236.1	240.1	246.0	256.9	275.6	289.5	303.3	342.8	400.1	486.1	604.6
120°	257.9	261.8	267.7	276.6	296.4	310.2	324.1	362.6	415.9	492.0	597.7
122.5°	278.6	281.6	287.5	297.4	317.1	331.5	345.8	381.4	429.8	498.9	593.8
125°	296.4	299.4	305.3	317.1	336.9	350.8	364.6	400.1	444.6	505.8	588.8
127.5°	311.2	315.2	323.1	335.9	354.7	369.0	383.3	417.9	458.4	512.8	585.9
130°	324.1	328.0	337.9	351.7	371.5	385.3	399.1	433.7	471.3	520.7	583.9
132.5°	335.9	340.8	351.7	366.5	387.3	401.1	414.9	447.5	484.1	528.6	582.9
135°	347.8	351.7	363.6	378.4	401.1	415.0	428.8	460.4	495.0	534.5	581.9
137.5°	358.6	363.6	375.4	391.2	414.0	426.8	439.6	471.3	503.9	540.4	581.9
140°	371.5	375.4	387.3	403.1	424.8	437.6	450.5	480.1	510.8	544.4	580.9
142.5°	384.3	387.3	398.1	414.0	434.7	446.6	458.4	487.1	516.7	547.3	580.9
145°	397.2	401.1	411.0	425.8	445.6	456.4	467.3	494.0	521.6	549.3	578.9
147.5°	411.0	414.0	423.8	437.7	454.5	464.4	474.2	499.9	524.6	550.3	576.0
150°	424.8	427.8	435.7	448.5	463.4	472.2	481.1	503.9	526.6	549.3	573.0
152.5°	438.7	439.6	447.5	458.4	472.2	480.2	488.1	507.8	527.6	547.3	568.1
155°	451.5	452.5	458.4	469.3	480.1	487.6	495.0	511.8	528.6	545.4	562.2
157.5°	462.4	463.4	468.3	478.2	487.1	493.5	499.9	514.7	528.6	541.4	556.2
160°	473.2	474.2	478.2	486.1	494.0	499.4	504.8	516.7	528.6	538.4	550.3
162.5°	484.1	483.1	487.1	493.0	499.9	503.8	507.8	517.7	527.6	535.5	545.4
165°	492.0	491.0	493.0	498.9	503.9	506.8	509.8	518.7	525.6	531.5	538.4
167.5°	498.9	497.9	499.9	503.9	507.8	509.8	511.8	518.7	524.6	527.6	532.5
170°	505.8	503.9	504.8	507.8	509.8	511.3	512.8	517.7	522.6	524.6	527.6
172.5°	509.8	508.8	507.8	510.8	511.8	512.8	513.7	516.7	519.7	520.7	521.6
175°	512.8	511.8	510.8	512.8	512.8	513.2	513.7	515.7	517.7	516.7	517.7
177.5°	514.7	512.8	511.8	513.7	513.7	513.7	513.7	514.7	516.7	514.7	513.7
180°	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7

TEST NUMBER: P1009928

CATALOG NUMBER: S122RDIP-B290D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5
2.5°	659.1	660.0	661.3	667.5	668.4	670.1	669.3	669.3	669.7	668.8	669.3
5°	687.4	688.7	695.4	702.9	704.6	702.9	705.1	708.2	708.2	708.2	707.3
7.5°	713.9	718.8	726.3	737.4	739.6	741.8	745.8	743.1	744.0	748.0	746.7
10°	739.6	746.7	755.1	764.4	769.2	772.3	774.1	778.1	787.4	776.8	780.7
12.5°	763.9	774.1	782.9	793.1	796.7	800.6	802.0	805.5	805.5	805.1	808.2
15°	779.8	789.1	797.1	803.7	804.6	803.7	802.8	803.3	804.6	799.3	802.4
17.5°	783.4	784.3	786.9	784.3	784.7	775.4	770.1	768.8	756.4	756.8	767.0
20°	766.1	751.1	747.1	732.5	723.7	699.8	698.9	692.3	666.2	674.1	672.4
22.5°	718.8	693.1	659.1	642.3	633.9	608.7	589.2	575.5	566.2	556.9	552.9
25°	656.4	614.9	566.6	533.5	528.6	505.2	469.3	452.5	432.6	426.4	437.0
27.5°	575.9	522.0	467.6	416.7	407.4	386.2	368.0	356.1	333.1	331.8	332.6
30°	466.7	412.3	366.7	333.5	310.5	300.8	288.8	280.0	270.7	274.3	275.1
32.5°	383.5	331.8	289.3	271.6	261.0	254.8	244.6	238.9	234.9	233.6	233.1
35°	304.8	270.3	251.2	234.0	227.8	223.4	215.9	213.2	209.7	210.1	210.1
37.5°	261.0	232.2	218.1	209.2	203.5	201.3	196.4	193.7	191.5	190.6	192.0
40°	225.2	205.2	196.4	188.4	183.6	182.7	180.0	176.9	174.3	174.7	176.1
42.5°	199.1	187.6	176.9	170.7	167.2	165.9	163.7	161.5	161.5	160.1	159.7
45°	178.3	169.0	160.1	154.4	152.2	150.4	147.7	147.3	145.5	146.0	146.4
47.5°	159.7	152.2	145.5	139.8	137.6	137.1	134.5	132.7	132.7	132.3	131.8
50°	142.9	135.4	129.6	126.5	123.4	122.5	122.1	121.6	120.8	120.8	121.2
52.5°	129.2	121.6	117.2	114.6	112.8	111.9	111.9	111.5	111.5	111.5	111.0
55°	114.1	107.9	104.4	103.5	102.6	102.2	101.7	100.9	100.4	101.3	100.4
57.5°	100.0	97.8	94.7	93.8	91.6	91.6	90.2	89.4	88.5	89.4	89.4
60°	88.9	85.8	84.0	81.4	79.6	77.9	75.6	75.2	74.3	73.9	73.4
62.5°	77.4	74.8	70.3	66.4	63.7	61.9	61.0	60.6	60.6	60.2	60.2
65°	64.6	58.4	56.2	54.9	54.4	54.0	53.1	52.6	53.1	52.6	53.1
67.5°	50.4	49.5	48.2	47.3	46.9	46.4	46.4	46.0	46.0	46.0	46.0
70°	43.8	41.6	41.1	40.3	40.3	39.8	39.8	39.8	39.8	39.4	40.3
72.5°	36.3	34.9	34.5	34.1	34.1	34.1	33.6	33.6	33.6	33.2	33.6
75°	29.6	29.2	28.3	28.3	27.9	28.3	27.9	27.9	27.4	27.9	27.9
77.5°	23.9	23.4	23.0	23.0	22.6	22.6	22.6	22.6	22.6	22.6	23.0
80°	18.1	17.7	17.3	17.7	17.3	17.7	17.3	17.3	17.7	17.3	17.3
82.5°	13.3	12.8	12.8	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4
85°	8.0	7.5	7.5	8.0	7.5	8.0	7.5	7.5	7.5	8.0	8.0
87.5°	3.5	4.0	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	4.0
90°	32.6	31.6	29.6	31.6	32.1	32.6	32.6	32.6	32.6	32.6	32.6
92.5°	127.4	99.8	85.0	74.1	70.2	66.2	65.2	61.3	62.2	60.3	62.2
95°	338.9	258.8	198.6	157.1	146.2	135.4	122.5	114.6	111.6	112.6	111.6
97.5°	636.2	529.5	422.8	323.1	293.5	263.8	225.3	205.5	194.6	188.7	194.6
100°	922.8	902.0	779.5	644.2	584.4	524.6	442.6	400.1	371.5	353.7	371.5
102.5°	1029.5	1146.0	1142.1	1052.2	988.0	923.7	832.9	752.8	715.3	689.6	715.3
105°	994.9	1200.4	1312.0	1324.9	1308.6	1292.3	1231.0	1169.7	1127.3	1113.4	1127.3
107.5°	921.8	1142.1	1308.1	1404.9	1424.6	1444.4	1443.4	1434.5	1421.7	1399.0	1421.7
110°	853.6	1062.1	1238.9	1365.4	1405.9	1446.4	1488.9	1507.6	1516.5	1515.5	1516.5

TEST NUMBER: P1009928

CATALOG NUMBER: S122RDIP-B290D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	806.2	988.9	1156.9	1294.2	1342.2	1390.1	1453.3	1487.9	1506.6	1513.6	1506.6
115°	768.6	931.6	1083.8	1213.2	1264.1	1315.0	1385.1	1430.6	1456.3	1465.1	1456.3
117.5°	742.9	884.2	1020.6	1141.1	1189.5	1237.9	1310.0	1358.4	1385.1	1392.0	1385.1
120°	723.2	850.6	973.1	1077.9	1122.8	1167.8	1236.9	1283.4	1312.0	1321.9	1312.0
122.5°	706.4	824.0	933.6	1031.4	1071.0	1110.5	1170.7	1216.2	1240.9	1248.8	1240.9
125°	690.6	798.3	900.0	987.0	1024.0	1061.1	1118.4	1155.9	1180.6	1188.5	1180.6
127.5°	675.8	772.6	866.4	949.4	984.0	1018.6	1069.0	1104.5	1126.3	1132.2	1126.3
130°	660.9	747.9	832.9	910.9	943.5	976.1	1024.5	1058.1	1077.9	1085.8	1077.9
132.5°	649.1	724.2	801.2	871.4	901.5	931.6	979.1	1012.7	1030.4	1037.4	1030.4
135°	638.2	702.4	767.6	832.9	860.6	888.2	930.7	963.3	981.0	985.0	981.0
137.5°	630.3	684.7	741.0	794.3	819.0	843.7	884.2	912.9	928.7	934.6	928.7
140°	623.4	667.9	715.3	760.7	782.4	804.2	835.8	861.5	876.3	882.2	876.3
142.5°	616.5	654.0	692.6	730.1	747.4	764.7	794.3	817.0	829.9	829.9	829.9
145°	610.6	641.2	673.8	704.4	718.8	733.1	756.8	773.6	783.5	786.4	783.5
147.5°	604.6	631.3	658.0	682.7	693.6	704.4	725.2	739.0	745.9	747.9	745.9
150°	596.7	620.4	642.2	662.9	671.8	680.7	695.5	707.4	713.3	714.3	713.3
152.5°	589.8	609.6	629.3	646.1	653.5	660.9	671.8	681.7	685.6	685.6	685.6
155°	580.9	599.7	615.5	630.3	635.8	641.2	652.1	659.0	662.9	660.9	662.9
157.5°	573.0	587.8	601.7	614.5	619.0	623.4	631.3	637.2	639.2	639.2	639.2
160°	564.1	577.0	587.8	598.7	602.2	605.6	612.5	617.5	618.5	618.5	618.5
162.5°	556.2	566.1	575.0	583.9	586.3	588.8	595.7	598.7	599.7	598.7	599.7
165°	547.3	555.2	562.2	569.1	571.0	573.0	577.0	580.9	580.9	579.9	580.9
167.5°	538.4	544.4	550.3	555.2	557.2	559.2	561.2	563.1	563.1	562.2	563.1
170°	531.5	536.5	539.4	543.4	544.4	545.4	546.3	549.3	548.3	546.3	548.3
172.5°	524.6	527.6	529.5	532.5	533.0	533.5	534.5	535.5	534.5	533.5	534.5
175°	518.7	521.6	522.6	523.6	524.1	524.6	524.6	525.6	524.6	522.6	524.6
177.5°	514.7	516.7	516.7	517.7	517.7	517.7	517.7	517.7	516.7	514.7	516.7
180°	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7

TEST NUMBER: P1009928

CATALOG NUMBER: S122RDIP-B290D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5
2.5°	671.0	667.9	667.0	667.9	667.0	667.5	664.4	652.9	656.0	651.1	653.8
5°	709.1	706.4	700.7	699.8	698.9	698.0	693.6	683.4	679.4	672.8	672.4
7.5°	745.3	745.3	740.9	737.8	733.8	730.7	725.0	710.0	703.8	695.8	691.4
10°	781.2	769.7	774.5	771.4	761.7	759.9	749.3	740.5	728.5	720.6	713.5
12.5°	806.8	803.3	798.9	796.2	793.6	787.8	780.7	758.2	752.0	736.1	728.1
15°	805.9	803.7	805.1	805.1	804.2	802.8	797.1	780.7	770.1	754.6	740.9
17.5°	762.6	768.3	774.1	778.1	786.9	790.9	796.2	786.5	779.8	766.6	752.0
20°	687.0	701.1	717.9	721.5	729.4	752.9	763.5	771.9	774.5	770.1	758.2
22.5°	581.7	593.6	634.3	633.4	644.9	672.8	703.8	729.0	748.9	759.9	755.5
25°	455.6	472.4	494.1	510.5	548.1	589.6	628.1	668.4	702.9	733.4	740.9
27.5°	344.6	366.7	384.0	405.6	424.6	473.7	523.3	586.1	626.4	684.3	714.4
30°	278.7	288.8	306.1	316.3	325.6	363.2	419.3	481.3	552.0	618.8	670.6
32.5°	238.0	245.1	257.9	262.3	272.0	297.3	332.6	389.3	462.2	543.2	611.3
35°	213.7	221.2	223.8	227.8	235.8	251.7	276.0	317.2	383.1	462.2	543.6
37.5°	192.9	196.8	204.4	207.0	209.7	221.6	238.0	266.7	310.5	375.5	465.8
40°	178.3	180.5	184.5	186.7	188.4	196.8	211.4	230.9	263.2	312.7	395.9
42.5°	162.8	165.4	168.1	170.7	173.0	179.6	188.4	207.0	228.7	266.3	326.4
45°	147.7	149.5	152.6	154.4	157.5	162.8	170.7	183.6	203.0	226.9	275.6
47.5°	134.0	136.2	137.6	139.8	142.0	147.7	155.3	163.7	179.6	203.0	238.4
50°	121.6	124.3	126.1	126.5	128.3	133.6	139.8	149.1	159.2	177.4	208.3
52.5°	112.8	113.2	114.6	116.3	115.9	119.0	124.7	131.8	142.4	157.0	179.6
55°	102.6	104.0	104.8	105.3	105.3	107.9	111.0	117.7	126.1	138.0	157.0
57.5°	89.8	91.1	93.8	94.7	96.0	97.3	98.6	103.1	110.1	121.6	137.1
60°	76.5	77.4	80.1	81.8	82.7	86.3	88.0	91.6	95.5	104.0	118.5
62.5°	61.5	62.4	63.7	65.5	67.2	72.5	77.0	80.5	83.6	89.4	101.3
65°	53.5	54.0	54.9	55.3	55.7	57.9	61.9	66.8	72.5	77.0	84.0
67.5°	46.4	46.9	47.3	48.2	48.7	49.1	50.9	52.2	57.9	64.1	69.4
70°	39.8	40.7	41.1	41.1	41.6	42.5	43.3	45.1	46.9	50.0	56.6
72.5°	33.6	34.1	34.9	34.9	34.9	35.8	36.7	37.6	38.5	40.3	42.9
75°	27.9	28.8	28.8	28.8	29.2	29.2	30.1	31.0	31.8	33.2	34.1
77.5°	23.0	23.0	23.0	23.0	23.4	23.4	23.9	24.8	25.2	25.7	26.5
80°	17.3	17.7	17.7	17.7	18.1	18.1	18.1	19.0	19.5	19.5	20.3
82.5°	12.8	12.8	12.8	13.3	12.8	13.3	13.3	13.7	13.3	13.7	14.2
85°	8.0	8.0	8.0	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.8
87.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.4	4.0	4.0
90°	32.6	32.6	32.6	32.1	31.6	29.6	31.6	32.6	33.6	32.6	26.7
92.5°	61.3	65.2	66.2	70.2	74.1	85.0	99.8	127.4	152.1	150.2	116.6
95°	114.6	122.5	135.4	146.2	157.1	198.6	258.8	338.9	387.3	342.8	228.2
97.5°	205.5	225.3	263.8	293.5	323.1	422.8	529.5	636.2	631.3	488.1	303.3
100°	400.1	442.6	524.6	584.4	644.2	779.5	902.0	922.8	780.5	537.5	324.1
102.5°	752.8	832.9	923.7	988.0	1052.2	1142.1	1146.0	1029.5	785.4	518.7	325.0
105°	1169.7	1231.0	1292.3	1308.6	1324.9	1312.0	1200.4	994.9	732.1	493.0	330.0
107.5°	1434.5	1443.4	1444.4	1424.6	1404.9	1308.1	1142.1	921.8	682.7	479.2	340.8
110°	1507.6	1488.9	1446.4	1405.9	1365.4	1238.9	1062.1	853.6	649.1	475.2	354.7

TEST NUMBER: P1009928

CATALOG NUMBER: S122RDIP-B290D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1487.9	1453.3	1390.1	1342.2	1294.2	1156.9	988.9	806.2	627.4	476.2	369.5
115°	1430.6	1385.1	1315.0	1264.1	1213.2	1083.8	931.6	768.6	612.5	480.1	384.3
117.5°	1358.4	1310.0	1237.9	1189.5	1141.1	1020.6	884.2	742.9	604.6	486.1	400.1
120°	1283.4	1236.9	1167.8	1122.8	1077.9	973.1	850.6	723.2	597.7	492.0	415.9
122.5°	1216.2	1170.7	1110.5	1071.0	1031.4	933.6	824.0	706.4	593.8	498.9	429.8
125°	1155.9	1118.4	1061.1	1024.0	987.0	900.0	798.3	690.6	588.8	505.8	444.6
127.5°	1104.5	1069.0	1018.6	984.0	949.4	866.4	772.6	675.8	585.9	512.8	458.4
130°	1058.1	1024.5	976.1	943.5	910.9	832.9	747.9	660.9	583.9	520.7	471.3
132.5°	1012.7	979.1	931.6	901.5	871.4	801.2	724.2	649.1	582.9	528.6	484.1
135°	963.3	930.7	888.2	860.6	832.9	767.6	702.4	638.2	581.9	534.5	495.0
137.5°	912.9	884.2	843.7	819.0	794.3	741.0	684.7	630.3	581.9	540.4	503.9
140°	861.5	835.8	804.2	782.4	760.7	715.3	667.9	623.4	580.9	544.4	510.8
142.5°	817.0	794.3	764.7	747.4	730.1	692.6	654.0	616.5	580.9	547.3	516.7
145°	773.6	756.8	733.1	718.8	704.4	673.8	641.2	610.6	578.9	549.3	521.6
147.5°	739.0	725.2	704.4	693.6	682.7	658.0	631.3	604.6	576.0	550.3	524.6
150°	707.4	695.5	680.7	671.8	662.9	642.2	620.4	596.7	573.0	549.3	526.6
152.5°	681.7	671.8	660.9	653.5	646.1	629.3	609.6	589.8	568.1	547.3	527.6
155°	659.0	652.1	641.2	635.8	630.3	615.5	599.7	580.9	562.2	545.4	528.6
157.5°	637.2	631.3	623.4	619.0	614.5	601.7	587.8	573.0	556.2	541.4	528.6
160°	617.5	612.5	605.6	602.2	598.7	587.8	577.0	564.1	550.3	538.4	528.6
162.5°	598.7	595.7	588.8	586.3	583.9	575.0	566.1	556.2	545.4	535.5	527.6
165°	580.9	577.0	573.0	571.0	569.1	562.2	555.2	547.3	538.4	531.5	525.6
167.5°	563.1	561.2	559.2	557.2	555.2	550.3	544.4	538.4	532.5	527.6	524.6
170°	549.3	546.3	545.4	544.4	543.4	539.4	536.5	531.5	527.6	524.6	522.6
172.5°	535.5	534.5	533.5	533.0	532.5	529.5	527.6	524.6	521.6	520.7	519.7
175°	525.6	524.6	524.6	524.1	523.6	522.6	521.6	518.7	517.7	516.7	517.7
177.5°	517.7	517.7	517.7	517.7	517.7	516.7	516.7	514.7	513.7	514.7	516.7
180°	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7

TEST NUMBER: P1009928

CATALOG NUMBER: S122RDIP-B290D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5
2.5°	649.8	647.6	647.6	646.3	646.3	639.2	639.2	641.4	638.7	635.6	631.2
5°	666.6	661.7	660.4	658.6	652.9	644.0	640.5	639.2	633.9	627.2	619.7
7.5°	682.5	674.6	670.6	666.6	659.1	646.7	639.6	634.8	626.8	616.6	606.9
10°	698.0	687.8	677.7	672.8	662.2	646.7	636.5	628.6	617.1	603.4	589.6
12.5°	712.2	690.9	689.2	679.4	664.0	646.3	630.8	619.3	604.7	588.8	572.8
15°	724.6	702.9	692.3	683.4	663.1	641.0	624.6	610.4	591.0	572.8	553.4
17.5°	730.7	707.3	700.2	685.6	664.8	636.1	614.0	596.7	575.5	553.8	531.7
20°	736.9	709.5	698.0	687.8	659.5	626.8	602.0	582.1	558.7	533.0	508.7
22.5°	740.0	709.5	695.8	681.6	654.2	616.6	587.4	564.0	536.6	510.5	481.3
25°	734.7	706.9	690.5	675.9	644.9	604.2	570.6	544.1	514.9	485.2	455.6
27.5°	721.5	700.7	681.6	666.6	632.1	588.3	552.9	522.8	492.8	459.6	429.5
30°	696.7	687.4	672.4	655.5	618.0	574.2	532.1	501.2	468.0	434.8	403.4
32.5°	658.2	666.2	656.4	641.8	601.1	554.7	510.0	478.6	442.3	406.5	377.8
35°	611.3	639.6	634.3	624.1	583.4	533.9	489.2	451.2	414.9	378.6	349.9
37.5°	560.0	602.9	607.3	601.1	563.1	512.7	463.6	426.4	389.3	352.5	323.4
40°	489.7	555.6	569.7	572.4	541.9	487.0	435.7	399.4	362.7	326.9	291.5
42.5°	425.1	508.2	525.9	537.0	514.9	461.8	410.0	369.8	333.5	301.2	265.8
45°	364.5	451.2	479.9	494.1	484.4	433.1	379.5	341.9	308.8	279.1	245.1
47.5°	302.1	389.3	429.5	452.1	452.1	403.9	350.3	313.2	281.3	256.1	226.0
50°	260.5	333.1	374.7	404.3	412.3	374.2	323.8	287.5	257.4	230.0	207.0
52.5°	222.1	287.1	321.6	352.5	375.5	342.4	294.2	261.4	231.8	206.1	188.0
55°	192.0	240.6	272.0	306.1	331.8	310.1	265.4	233.6	207.9	186.7	171.2
57.5°	163.2	205.7	231.3	261.4	288.8	272.5	236.7	209.2	186.7	168.1	154.4
60°	138.9	173.4	193.3	216.7	250.8	239.3	209.7	184.5	166.3	149.5	138.0
62.5°	118.1	145.5	162.3	179.1	210.1	204.8	181.8	162.3	146.9	132.7	123.0
65°	96.9	119.4	132.7	147.3	172.1	174.3	155.7	142.0	127.8	115.5	106.6
67.5°	78.3	96.0	107.9	120.3	140.2	146.4	133.6	122.1	110.1	100.0	92.0
70°	63.3	75.6	84.5	94.2	110.6	118.1	111.5	103.5	93.8	85.4	78.3
72.5°	50.0	57.9	63.3	70.8	84.0	91.6	91.1	84.0	77.0	71.2	65.5
75°	36.7	42.9	47.3	52.2	62.8	69.9	71.7	68.6	61.5	57.1	52.6
77.5°	27.9	31.4	33.6	37.2	44.7	50.9	53.5	52.6	47.8	44.2	41.1
80°	21.2	22.1	23.0	24.3	30.5	36.3	38.0	37.6	34.9	33.6	30.1
82.5°	15.0	15.5	15.9	16.4	18.6	23.4	25.2	26.1	23.9	22.6	19.5
85°	8.8	9.3	9.3	10.2	10.6	11.9	15.0	15.0	14.6	12.8	12.4
87.5°	4.4	4.4	4.0	4.0	4.4	4.9	5.8	6.6	5.8	5.3	4.9
90°	19.8	14.8	13.4	11.9	9.9	7.9	4.0	1.0	4.0	7.9	9.9
92.5°	79.0	52.4	47.0	41.5	33.6	28.7	20.7	14.8	20.7	28.7	33.6
95°	142.3	96.8	84.9	73.1	57.3	48.4	38.5	34.6	38.5	48.4	57.3
97.5°	183.8	125.5	112.2	98.8	81.0	68.2	57.3	51.4	57.3	68.2	81.0
100°	203.5	151.2	137.4	123.5	103.7	87.9	79.0	76.1	79.0	87.9	103.7
102.5°	221.3	173.9	160.0	146.2	125.5	109.7	100.8	98.8	100.8	109.7	125.5
105°	242.1	195.6	181.8	168.0	146.2	131.4	124.5	120.5	124.5	131.4	146.2
107.5°	262.8	217.4	203.6	189.7	168.0	154.1	147.2	144.2	147.2	154.1	168.0
110°	283.5	240.1	225.8	211.4	190.7	177.8	171.9	168.0	171.9	177.8	190.7

TEST NUMBER: P1009928

CATALOG NUMBER: S122RDIP-B290D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	303.3	261.8	247.0	232.2	212.4	200.6	193.6	189.7	193.6	200.6	212.4
115°	324.1	281.6	268.2	254.9	235.1	223.3	217.4	212.4	217.4	223.3	235.1
117.5°	342.8	303.3	289.5	275.6	256.9	246.0	240.1	236.1	240.1	246.0	256.9
120°	362.6	324.1	310.2	296.4	276.6	267.7	261.8	257.9	261.8	267.7	276.6
122.5°	381.4	345.8	331.5	317.1	297.4	287.5	281.6	278.6	281.6	287.5	297.4
125°	400.1	364.6	350.8	336.9	317.1	305.3	299.4	296.4	299.4	305.3	317.1
127.5°	417.9	383.3	369.0	354.7	335.9	323.1	315.2	311.2	315.2	323.1	335.9
130°	433.7	399.1	385.3	371.5	351.7	337.9	328.0	324.1	328.0	337.9	351.7
132.5°	447.5	414.9	401.1	387.3	366.5	351.7	340.8	335.9	340.8	351.7	366.5
135°	460.4	428.8	415.0	401.1	378.4	363.6	351.7	347.8	351.7	363.6	378.4
137.5°	471.3	439.6	426.8	414.0	391.2	375.4	363.6	358.6	363.6	375.4	391.2
140°	480.1	450.5	437.6	424.8	403.1	387.3	375.4	371.5	375.4	387.3	403.1
142.5°	487.1	458.4	446.6	434.7	414.0	398.1	387.3	384.3	387.3	398.1	414.0
145°	494.0	467.3	456.4	445.6	425.8	411.0	401.1	397.2	401.1	411.0	425.8
147.5°	499.9	474.2	464.4	454.5	437.7	423.8	414.0	411.0	414.0	423.8	437.7
150°	503.9	481.1	472.2	463.4	448.5	435.7	427.8	424.8	427.8	435.7	448.5
152.5°	507.8	488.1	480.2	472.2	458.4	447.5	439.6	438.7	439.6	447.5	458.4
155°	511.8	495.0	487.6	480.1	469.3	458.4	452.5	451.5	452.5	458.4	469.3
157.5°	514.7	499.9	493.5	487.1	478.2	468.3	463.4	462.4	463.4	468.3	478.2
160°	516.7	504.8	499.4	494.0	486.1	478.2	474.2	473.2	474.2	478.2	486.1
162.5°	517.7	507.8	503.8	499.9	493.0	487.1	483.1	484.1	483.1	487.1	493.0
165°	518.7	509.8	506.8	503.9	498.9	493.0	491.0	492.0	491.0	493.0	498.9
167.5°	518.7	511.8	509.8	507.8	503.9	499.9	497.9	498.9	497.9	499.9	503.9
170°	517.7	512.8	511.3	509.8	507.8	504.8	503.9	505.8	503.9	504.8	507.8
172.5°	516.7	513.7	512.8	511.8	510.8	507.8	508.8	509.8	508.8	507.8	510.8
175°	515.7	513.7	513.2	512.8	512.8	510.8	511.8	512.8	511.8	510.8	512.8
177.5°	514.7	513.7	513.7	513.7	513.7	511.8	512.8	514.7	512.8	511.8	513.7
180°	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7

TEST NUMBER: P1009928

CATALOG NUMBER: S122RDIP-B290D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5
2.5°	629.5	629.9	631.2	627.2	621.0	618.4	610.4	609.1	607.8	607.8	609.1
5°	615.3	613.5	614.0	606.4	597.6	592.3	581.2	583.0	577.3	573.7	574.6
7.5°	599.8	594.9	594.5	584.8	573.7	564.0	552.5	549.8	544.5	538.3	535.7
10°	580.4	576.8	570.2	559.1	545.0	537.0	521.5	512.2	510.9	501.6	498.1
12.5°	560.4	554.3	547.6	532.1	516.2	503.4	491.9	481.7	474.6	466.7	461.4
15°	537.4	529.9	522.4	506.0	487.5	474.6	457.4	442.3	421.6	405.2	395.9
17.5°	512.2	503.8	493.7	475.5	457.4	439.7	407.8	390.1	375.5	365.8	360.1
20°	486.1	476.8	466.7	448.5	417.1	386.2	368.5	354.8	345.9	336.2	329.1
22.5°	458.7	449.0	437.9	409.6	376.4	354.8	341.0	328.2	315.4	310.1	306.5
25°	433.1	424.2	410.0	371.6	345.5	325.6	310.1	301.7	295.0	288.0	281.3
27.5°	406.5	390.1	370.2	337.9	321.6	301.2	290.2	284.0	272.5	267.6	264.5
30°	374.7	356.5	337.5	314.5	295.5	281.3	271.2	261.0	254.3	249.5	244.2
32.5°	342.4	325.1	313.2	289.3	275.1	260.5	250.8	244.6	234.9	231.8	229.6
35°	314.5	299.9	289.3	269.8	256.6	243.3	236.2	226.9	220.7	215.0	211.4
37.5°	287.1	279.1	268.1	251.7	237.5	226.9	217.2	214.1	205.7	202.6	199.1
40°	268.1	256.1	246.8	232.7	220.7	209.2	203.0	196.0	190.2	185.3	184.0
42.5°	245.1	236.2	230.9	215.4	203.0	196.4	188.9	180.9	176.5	172.5	167.6
45°	227.8	219.8	212.3	199.9	188.9	180.5	173.8	168.5	161.0	159.2	151.7
47.5°	209.7	201.7	196.0	183.6	173.4	165.4	160.6	153.5	147.3	143.3	139.8
50°	191.5	184.9	179.6	169.0	160.1	151.7	145.1	138.0	135.4	128.7	126.5
52.5°	174.3	169.9	164.1	153.9	145.1	138.0	130.9	125.2	121.2	117.7	115.0
55°	159.7	152.6	150.0	138.9	131.4	123.9	117.7	114.1	109.3	107.0	104.8
57.5°	143.3	139.3	134.9	126.5	118.1	111.0	106.6	101.3	98.6	96.0	94.2
60°	129.2	123.4	119.9	112.8	105.3	98.6	94.7	90.7	87.1	84.9	81.4
62.5°	112.8	108.4	106.2	98.6	92.4	86.3	82.7	78.7	76.1	72.1	67.7
65°	98.6	95.1	92.4	86.3	80.5	74.8	71.2	66.4	62.8	60.6	60.2
67.5°	86.3	83.6	79.6	73.9	68.1	63.7	59.7	55.7	55.3	54.4	54.4
70°	72.5	69.9	67.7	61.5	56.6	51.8	50.9	49.5	48.2	47.8	46.9
72.5°	60.6	58.4	55.7	50.4	45.6	44.2	43.3	42.5	41.1	40.7	40.3
75°	49.1	46.0	44.2	39.4	38.0	37.2	36.3	34.9	34.1	33.6	32.7
77.5°	37.6	34.5	34.5	31.8	31.0	29.6	28.8	27.9	27.4	26.5	26.5
80°	26.5	26.5	25.7	24.3	23.0	22.6	21.2	20.8	20.3	20.8	19.9
82.5°	19.5	17.7	17.7	16.8	15.9	15.5	14.6	14.6	14.2	14.2	14.2
85°	11.1	11.1	10.6	9.7	9.3	9.3	8.8	8.8	8.4	8.4	8.0
87.5°	4.4	4.0	4.4	4.0	4.0	3.5	3.5	3.5	3.1	3.5	3.1
90°	11.9	13.4	14.8	19.8	26.7	32.6	33.6	32.6	31.6	29.6	31.6
92.5°	41.5	47.0	52.4	79.0	116.6	150.2	152.1	127.4	99.8	85.0	74.1
95°	73.1	84.9	96.8	142.3	228.2	342.8	387.3	338.9	258.8	198.6	157.1
97.5°	98.8	112.2	125.5	183.8	303.3	488.1	631.3	636.2	529.5	422.8	323.1
100°	123.5	137.4	151.2	203.5	324.1	537.5	780.5	922.8	902.0	779.5	644.2
102.5°	146.2	160.0	173.9	221.3	325.0	518.7	785.4	1029.5	1146.0	1142.1	1052.2
105°	168.0	181.8	195.6	242.1	330.0	493.0	732.1	994.9	1200.4	1312.0	1324.9
107.5°	189.7	203.6	217.4	262.8	340.8	479.2	682.7	921.8	1142.1	1308.1	1404.9
110°	211.4	225.8	240.1	283.5	354.7	475.2	649.1	853.6	1062.1	1238.9	1365.4

TEST NUMBER: P1009928

CATALOG NUMBER: S122RDIP-B290D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	232.2	247.0	261.8	303.3	369.5	476.2	627.4	806.2	988.9	1156.9	1294.2
115°	254.9	268.2	281.6	324.1	384.3	480.1	612.5	768.6	931.6	1083.8	1213.2
117.5°	275.6	289.5	303.3	342.8	400.1	486.1	604.6	742.9	884.2	1020.6	1141.1
120°	296.4	310.2	324.1	362.6	415.9	492.0	597.7	723.2	850.6	973.1	1077.9
122.5°	317.1	331.5	345.8	381.4	429.8	498.9	593.8	706.4	824.0	933.6	1031.4
125°	336.9	350.8	364.6	400.1	444.6	505.8	588.8	690.6	798.3	900.0	987.0
127.5°	354.7	369.0	383.3	417.9	458.4	512.8	585.9	675.8	772.6	866.4	949.4
130°	371.5	385.3	399.1	433.7	471.3	520.7	583.9	660.9	747.9	832.9	910.9
132.5°	387.3	401.1	414.9	447.5	484.1	528.6	582.9	649.1	724.2	801.2	871.4
135°	401.1	415.0	428.8	460.4	495.0	534.5	581.9	638.2	702.4	767.6	832.9
137.5°	414.0	426.8	439.6	471.3	503.9	540.4	581.9	630.3	684.7	741.0	794.3
140°	424.8	437.6	450.5	480.1	510.8	544.4	580.9	623.4	667.9	715.3	760.7
142.5°	434.7	446.6	458.4	487.1	516.7	547.3	580.9	616.5	654.0	692.6	730.1
145°	445.6	456.4	467.3	494.0	521.6	549.3	578.9	610.6	641.2	673.8	704.4
147.5°	454.5	464.4	474.2	499.9	524.6	550.3	576.0	604.6	631.3	658.0	682.7
150°	463.4	472.2	481.1	503.9	526.6	549.3	573.0	596.7	620.4	642.2	662.9
152.5°	472.2	480.2	488.1	507.8	527.6	547.3	568.1	589.8	609.6	629.3	646.1
155°	480.1	487.6	495.0	511.8	528.6	545.4	562.2	580.9	599.7	615.5	630.3
157.5°	487.1	493.5	499.9	514.7	528.6	541.4	556.2	573.0	587.8	601.7	614.5
160°	494.0	499.4	504.8	516.7	528.6	538.4	550.3	564.1	577.0	587.8	598.7
162.5°	499.9	503.8	507.8	517.7	527.6	535.5	545.4	556.2	566.1	575.0	583.9
165°	503.9	506.8	509.8	518.7	525.6	531.5	538.4	547.3	555.2	562.2	569.1
167.5°	507.8	509.8	511.8	518.7	524.6	527.6	532.5	538.4	544.4	550.3	555.2
170°	509.8	511.3	512.8	517.7	522.6	524.6	527.6	531.5	536.5	539.4	543.4
172.5°	511.8	512.8	513.7	516.7	519.7	520.7	521.6	524.6	527.6	529.5	532.5
175°	512.8	513.2	513.7	515.7	517.7	516.7	517.7	518.7	521.6	522.6	523.6
177.5°	513.7	513.7	513.7	514.7	516.7	514.7	513.7	514.7	516.7	516.7	517.7
180°	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7

TEST NUMBER: P1009928

CATALOG NUMBER: S122RDIP-B290D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5
2.5°	609.1	608.2	605.6	606.4	605.1	605.1	604.2	604.2	604.2	606.4	605.1
5°	575.9	572.8	569.7	568.4	567.1	565.8	565.8	565.3	569.3	568.4	571.9
7.5°	534.8	533.9	527.7	527.7	525.5	524.6	526.8	527.3	527.7	528.6	530.8
10°	498.1	495.9	487.0	487.9	486.6	484.8	486.1	485.2	488.3	489.2	488.3
12.5°	454.7	450.7	441.0	436.1	430.8	426.9	431.7	428.2	440.6	444.1	453.8
15°	397.2	389.7	383.1	383.1	378.2	374.7	376.9	380.9	383.5	387.5	389.3
17.5°	358.7	355.6	350.3	347.2	345.9	344.6	344.6	346.4	352.1	351.7	355.2
20°	326.0	324.2	321.6	317.6	316.3	315.4	315.4	315.4	319.4	322.9	325.1
22.5°	303.4	302.1	300.3	295.0	292.4	291.5	293.7	295.0	298.1	300.8	303.0
25°	280.9	277.8	274.7	272.9	271.6	271.6	272.5	272.9	274.3	275.6	278.2
27.5°	262.3	260.1	255.7	250.8	250.8	249.5	250.4	251.2	254.3	258.8	261.0
30°	241.5	241.1	239.3	237.5	235.8	234.9	236.7	238.0	238.4	240.6	240.6
32.5°	226.5	223.4	220.3	218.5	217.6	217.2	217.6	219.4	219.4	222.1	225.2
35°	211.4	209.7	206.6	203.5	202.6	200.4	202.1	203.9	207.0	208.3	209.7
37.5°	195.1	192.9	191.5	190.6	188.9	189.3	188.0	190.6	193.3	192.9	193.7
40°	182.7	178.7	174.7	174.3	173.8	173.4	173.4	173.8	175.6	177.4	180.0
42.5°	166.8	165.4	161.9	158.4	157.5	156.6	155.7	157.5	161.0	164.1	165.4
45°	150.4	148.6	147.7	145.1	143.3	142.9	142.0	144.2	147.3	148.6	149.5
47.5°	135.4	134.9	132.3	132.7	131.4	131.8	131.4	132.7	132.7	134.0	134.9
50°	125.2	123.9	122.5	121.6	120.3	120.3	119.9	120.3	122.1	123.9	123.4
52.5°	115.0	112.8	112.4	111.9	111.0	111.9	110.6	111.0	112.8	113.7	113.2
55°	103.1	102.6	101.7	100.9	100.4	100.0	100.0	100.0	101.7	103.1	103.5
57.5°	93.8	91.6	89.8	89.8	88.0	87.6	88.5	88.9	90.2	91.1	92.0
60°	80.9	80.1	77.4	76.1	73.4	73.0	73.0	74.8	77.0	80.1	80.9
62.5°	67.2	65.9	65.5	65.5	65.5	65.5	65.5	65.5	65.5	65.9	65.9
65°	59.7	60.2	59.7	59.3	59.7	59.7	59.3	59.3	59.3	59.7	60.2
67.5°	53.5	53.1	53.5	53.1	52.6	52.6	52.2	52.6	53.1	53.5	53.5
70°	46.4	46.4	46.0	46.4	46.0	45.6	45.1	45.1	46.0	46.4	46.4
72.5°	39.8	39.8	39.4	39.4	38.5	38.5	38.9	38.5	38.5	39.8	39.8
75°	33.2	32.7	32.3	32.3	31.8	31.8	31.8	31.4	32.3	32.3	32.7
77.5°	26.1	26.1	26.1	25.7	25.7	25.2	25.2	25.7	25.7	25.7	26.1
80°	19.9	19.9	19.9	19.5	19.0	19.0	19.0	19.0	19.0	19.5	19.0
82.5°	13.7	13.7	13.7	13.7	13.7	13.3	13.3	13.3	13.7	13.7	13.3
85°	8.4	8.0	8.4	8.4	8.0	8.4	8.0	8.0	7.5	7.5	8.0
87.5°	3.5	3.1	2.7	2.7	3.1	2.7	2.7	2.7	3.1	2.7	2.7
90°	32.1	32.6	32.6	32.6	32.6	32.6	32.6	32.6	32.6	32.6	32.1
92.5°	70.2	66.2	65.2	61.3	62.2	60.3	62.2	61.3	65.2	66.2	70.2
95°	146.2	135.4	122.5	114.6	111.6	112.6	111.6	114.6	122.5	135.4	146.2
97.5°	293.5	263.8	225.3	205.5	194.6	188.7	194.6	205.5	225.3	263.8	293.5
100°	584.4	524.6	442.6	400.1	371.5	353.7	371.5	400.1	442.6	524.6	584.4
102.5°	988.0	923.7	832.9	752.8	715.3	689.6	715.3	752.8	832.9	923.7	988.0
105°	1308.6	1292.3	1231.0	1169.7	1127.3	1113.4	1127.3	1169.7	1231.0	1292.3	1308.6
107.5°	1424.6	1444.4	1443.4	1434.5	1421.7	1399.0	1421.7	1434.5	1443.4	1444.4	1424.6
110°	1405.9	1446.4	1488.9	1507.6	1516.5	1515.5	1516.5	1507.6	1488.9	1446.4	1405.9

TEST NUMBER: P1009928

CATALOG NUMBER: S122RDIP-B290D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1342.2	1390.1	1453.3	1487.9	1506.6	1513.6	1506.6	1487.9	1453.3	1390.1	1342.2
115°	1264.1	1315.0	1385.1	1430.6	1456.3	1465.1	1456.3	1430.6	1385.1	1315.0	1264.1
117.5°	1189.5	1237.9	1310.0	1358.4	1385.1	1392.0	1385.1	1358.4	1310.0	1237.9	1189.5
120°	1122.8	1167.8	1236.9	1283.4	1312.0	1321.9	1312.0	1283.4	1236.9	1167.8	1122.8
122.5°	1071.0	1110.5	1170.7	1216.2	1240.9	1248.8	1240.9	1216.2	1170.7	1110.5	1071.0
125°	1024.0	1061.1	1118.4	1155.9	1180.6	1188.5	1180.6	1155.9	1118.4	1061.1	1024.0
127.5°	984.0	1018.6	1069.0	1104.5	1126.3	1132.2	1126.3	1104.5	1069.0	1018.6	984.0
130°	943.5	976.1	1024.5	1058.1	1077.9	1085.8	1077.9	1058.1	1024.5	976.1	943.5
132.5°	901.5	931.6	979.1	1012.7	1030.4	1037.4	1030.4	1012.7	979.1	931.6	901.5
135°	860.6	888.2	930.7	963.3	981.0	985.0	981.0	963.3	930.7	888.2	860.6
137.5°	819.0	843.7	884.2	912.9	928.7	934.6	928.7	912.9	884.2	843.7	819.0
140°	782.4	804.2	835.8	861.5	876.3	882.2	876.3	861.5	835.8	804.2	782.4
142.5°	747.4	764.7	794.3	817.0	829.9	829.9	829.9	817.0	794.3	764.7	747.4
145°	718.8	733.1	756.8	773.6	783.5	786.4	783.5	773.6	756.8	733.1	718.8
147.5°	693.6	704.4	725.2	739.0	745.9	747.9	745.9	739.0	725.2	704.4	693.6
150°	671.8	680.7	695.5	707.4	713.3	714.3	713.3	707.4	695.5	680.7	671.8
152.5°	653.5	660.9	671.8	681.7	685.6	685.6	685.6	681.7	671.8	660.9	653.5
155°	635.8	641.2	652.1	659.0	662.9	660.9	662.9	659.0	652.1	641.2	635.8
157.5°	619.0	623.4	631.3	637.2	639.2	639.2	639.2	637.2	631.3	623.4	619.0
160°	602.2	605.6	612.5	617.5	618.5	618.5	618.5	617.5	612.5	605.6	602.2
162.5°	586.3	588.8	595.7	598.7	599.7	598.7	599.7	598.7	595.7	588.8	586.3
165°	571.0	573.0	577.0	580.9	580.9	579.9	580.9	580.9	577.0	573.0	571.0
167.5°	557.2	559.2	561.2	563.1	563.1	562.2	563.1	563.1	561.2	559.2	557.2
170°	544.4	545.4	546.3	549.3	548.3	546.3	548.3	549.3	546.3	545.4	544.4
172.5°	533.0	533.5	534.5	535.5	534.5	533.5	534.5	535.5	534.5	533.5	533.0
175°	524.1	524.6	524.6	525.6	524.6	522.6	524.6	525.6	524.6	524.6	524.1
177.5°	517.7	517.7	517.7	517.7	516.7	514.7	516.7	517.7	517.7	517.7	517.7
180°	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7

TEST NUMBER: P1009928

CATALOG NUMBER: S122RDIP-B290D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5
2.5°	606.4	608.7	607.8	602.9	607.8	609.1	611.8	614.4	616.2	618.8	621.0
5°	568.4	572.8	575.5	572.8	581.7	583.0	589.2	592.7	598.0	602.5	606.0
7.5°	532.6	536.1	541.4	542.3	547.6	553.8	562.7	571.5	579.9	584.3	588.3
10°	494.1	500.3	508.2	506.5	514.4	524.2	533.5	547.6	554.7	562.7	569.7
12.5°	455.6	459.6	470.2	473.7	485.2	492.8	505.6	514.4	532.1	541.4	547.6
15°	388.4	404.7	418.0	433.9	449.0	463.1	474.6	490.6	506.0	513.1	523.3
17.5°	357.9	365.4	373.3	381.3	400.8	426.0	446.3	463.6	476.8	486.1	498.1
20°	326.0	333.5	342.4	349.9	361.8	380.0	405.2	434.8	450.7	460.5	472.0
22.5°	303.4	310.5	316.3	322.9	332.2	345.5	364.5	401.2	422.4	434.4	444.6
25°	279.1	288.0	294.2	299.0	306.5	321.1	336.6	357.4	395.5	404.7	418.9
27.5°	262.3	265.0	272.0	279.6	287.1	295.0	311.0	328.7	354.3	374.7	391.9
30°	242.4	249.0	255.7	258.8	265.4	276.9	286.6	305.7	325.6	341.5	362.3
32.5°	227.4	231.3	235.8	243.3	249.5	257.4	267.2	283.1	299.9	310.1	326.0
35°	210.6	213.2	222.5	225.6	231.8	239.7	249.5	261.9	280.0	288.0	299.5
37.5°	194.6	200.8	203.5	210.6	216.3	224.3	231.3	245.5	257.4	266.7	277.3
40°	182.2	184.9	189.8	196.0	200.8	207.0	215.9	226.0	238.9	246.4	255.7
42.5°	167.2	169.4	175.6	179.1	187.1	192.9	198.2	210.6	222.1	227.8	237.1
45°	150.8	156.1	160.1	167.2	171.6	178.7	185.3	194.2	204.8	211.4	216.7
47.5°	136.7	142.0	146.0	152.6	159.7	162.8	169.9	179.1	188.9	194.2	201.7
50°	125.2	127.0	134.5	137.6	145.1	151.3	156.1	164.1	174.7	177.8	184.0
52.5°	114.1	115.5	120.3	124.3	130.9	136.2	142.4	150.0	158.8	163.7	168.5
55°	104.4	105.3	107.5	111.9	116.3	123.0	128.7	135.8	143.3	148.6	153.0
57.5°	93.3	95.1	96.9	99.5	104.0	110.1	116.3	123.0	129.2	132.7	138.5
60°	80.5	83.2	86.3	89.4	92.4	96.9	104.0	110.1	115.9	119.0	123.4
62.5°	66.8	72.1	74.8	78.3	80.9	84.9	90.2	97.3	101.3	105.3	108.8
65°	60.2	60.6	61.0	64.6	69.4	73.4	78.3	83.6	89.8	92.4	95.1
67.5°	53.5	54.0	54.9	55.3	57.1	61.5	66.8	72.5	77.4	79.2	81.8
70°	46.9	46.9	48.7	49.1	49.5	50.0	54.4	60.2	64.6	66.8	69.9
72.5°	39.8	40.3	41.1	41.6	42.5	43.3	44.7	47.8	53.1	55.3	58.8
75°	32.7	33.2	33.6	34.1	35.4	35.8	37.2	38.9	41.1	43.8	46.0
77.5°	26.1	26.1	26.5	27.4	28.3	28.8	30.1	31.0	31.8	33.2	34.9
80°	19.5	19.9	19.9	20.8	20.8	21.2	21.7	23.0	23.9	24.8	25.7
82.5°	13.3	14.2	14.2	14.2	14.6	15.0	15.5	15.5	16.4	16.8	18.1
85°	8.0	8.4	8.4	8.4	8.0	8.8	8.8	9.3	9.3	9.3	9.7
87.5°	3.1	2.7	3.1	3.1	3.1	3.5	3.1	3.1	3.5	4.0	4.0
90°	31.6	29.6	31.6	32.6	33.6	32.6	26.7	19.8	14.8	13.4	11.9
92.5°	74.1	85.0	99.8	127.4	152.1	150.2	116.6	79.0	52.4	47.0	41.5
95°	157.1	198.6	258.8	338.9	387.3	342.8	228.2	142.3	96.8	84.9	73.1
97.5°	323.1	422.8	529.5	636.2	631.3	488.1	303.3	183.8	125.5	112.2	98.8
100°	644.2	779.5	902.0	922.8	780.5	537.5	324.1	203.5	151.2	137.4	123.5
102.5°	1052.2	1142.1	1146.0	1029.5	785.4	518.7	325.0	221.3	173.9	160.0	146.2
105°	1324.9	1312.0	1200.4	994.9	732.1	493.0	330.0	242.1	195.6	181.8	168.0
107.5°	1404.9	1308.1	1142.1	921.8	682.7	479.2	340.8	262.8	217.4	203.6	189.7
110°	1365.4	1238.9	1062.1	853.6	649.1	475.2	354.7	283.5	240.1	225.8	211.4

TEST NUMBER: P1009928

CATALOG NUMBER: S122RDIP-B290D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1294.2	1156.9	988.9	806.2	627.4	476.2	369.5	303.3	261.8	247.0	232.2
115°	1213.2	1083.8	931.6	768.6	612.5	480.1	384.3	324.1	281.6	268.2	254.9
117.5°	1141.1	1020.6	884.2	742.9	604.6	486.1	400.1	342.8	303.3	289.5	275.6
120°	1077.9	973.1	850.6	723.2	597.7	492.0	415.9	362.6	324.1	310.2	296.4
122.5°	1031.4	933.6	824.0	706.4	593.8	498.9	429.8	381.4	345.8	331.5	317.1
125°	987.0	900.0	798.3	690.6	588.8	505.8	444.6	400.1	364.6	350.8	336.9
127.5°	949.4	866.4	772.6	675.8	585.9	512.8	458.4	417.9	383.3	369.0	354.7
130°	910.9	832.9	747.9	660.9	583.9	520.7	471.3	433.7	399.1	385.3	371.5
132.5°	871.4	801.2	724.2	649.1	582.9	528.6	484.1	447.5	414.9	401.1	387.3
135°	832.9	767.6	702.4	638.2	581.9	534.5	495.0	460.4	428.8	415.0	401.1
137.5°	794.3	741.0	684.7	630.3	581.9	540.4	503.9	471.3	439.6	426.8	414.0
140°	760.7	715.3	667.9	623.4	580.9	544.4	510.8	480.1	450.5	437.6	424.8
142.5°	730.1	692.6	654.0	616.5	580.9	547.3	516.7	487.1	458.4	446.6	434.7
145°	704.4	673.8	641.2	610.6	578.9	549.3	521.6	494.0	467.3	456.4	445.6
147.5°	682.7	658.0	631.3	604.6	576.0	550.3	524.6	499.9	474.2	464.4	454.5
150°	662.9	642.2	620.4	596.7	573.0	549.3	526.6	503.9	481.1	472.2	463.4
152.5°	646.1	629.3	609.6	589.8	568.1	547.3	527.6	507.8	488.1	480.2	472.2
155°	630.3	615.5	599.7	580.9	562.2	545.4	528.6	511.8	495.0	487.6	480.1
157.5°	614.5	601.7	587.8	573.0	556.2	541.4	528.6	514.7	499.9	493.5	487.1
160°	598.7	587.8	577.0	564.1	550.3	538.4	528.6	516.7	504.8	499.4	494.0
162.5°	583.9	575.0	566.1	556.2	545.4	535.5	527.6	517.7	507.8	503.8	499.9
165°	569.1	562.2	555.2	547.3	538.4	531.5	525.6	518.7	509.8	506.8	503.9
167.5°	555.2	550.3	544.4	538.4	532.5	527.6	524.6	518.7	511.8	509.8	507.8
170°	543.4	539.4	536.5	531.5	527.6	524.6	522.6	517.7	512.8	511.3	509.8
172.5°	532.5	529.5	527.6	524.6	521.6	520.7	519.7	516.7	513.7	512.8	511.8
175°	523.6	522.6	521.6	518.7	517.7	516.7	517.7	515.7	513.7	513.2	512.8
177.5°	517.7	516.7	516.7	514.7	513.7	514.7	516.7	514.7	513.7	513.7	513.7
180°	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7

TEST NUMBER: P1009928

CATALOG NUMBER: S122RDIP-B290D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	636.5	636.5	636.5	636.5
2.5°	625.0	623.7	631.7	640.5
5°	612.2	614.4	624.6	637.0
7.5°	598.9	603.8	615.7	632.1
10°	580.4	589.2	607.3	624.1
12.5°	562.2	574.2	591.4	611.3
15°	541.9	555.1	576.4	600.3
17.5°	519.3	534.3	559.1	585.2
20°	495.4	515.3	541.4	569.7
22.5°	468.9	492.8	519.8	551.2
25°	443.2	469.3	496.3	532.6
27.5°	418.0	443.7	473.7	510.5
30°	392.8	416.2	448.5	487.9
32.5°	365.8	390.1	424.2	464.5
35°	341.0	365.4	397.2	437.0
37.5°	314.5	340.6	371.1	412.3
40°	283.5	314.1	343.7	383.1
42.5°	257.9	290.2	318.9	356.1
45°	237.5	268.1	291.9	328.2
47.5°	218.5	243.3	267.6	301.2
50°	200.4	219.4	244.6	274.7
52.5°	181.8	198.2	219.8	248.2
55°	165.0	180.5	199.9	221.6
57.5°	149.5	160.6	180.0	199.5
60°	132.3	143.8	158.8	175.2
62.5°	117.7	126.5	140.7	154.4
65°	102.2	110.6	121.2	134.0
67.5°	88.0	95.5	104.0	114.1
70°	75.2	80.9	87.1	96.0
72.5°	61.5	67.7	73.4	80.5
75°	50.4	53.1	57.9	62.8
77.5°	38.9	42.5	45.1	49.1
80°	27.9	31.0	31.8	34.9
82.5°	18.6	20.3	22.1	23.0
85°	10.6	11.5	13.3	13.7
87.5°	4.0	4.4	5.3	6.2
90°	9.9	7.9	4.0	1.0
92.5°	33.6	28.7	20.7	14.8
95°	57.3	48.4	38.5	34.6
97.5°	81.0	68.2	57.3	51.4
100°	103.7	87.9	79.0	76.1
102.5°	125.5	109.7	100.8	98.8
105°	146.2	131.4	124.5	120.5
107.5°	168.0	154.1	147.2	144.2
110°	190.7	177.8	171.9	168.0

TEST NUMBER: P1009928

CATALOG NUMBER: S122RDIP-B290D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	212.4	200.6	193.6	189.7
115°	235.1	223.3	217.4	212.4
117.5°	256.9	246.0	240.1	236.1
120°	276.6	267.7	261.8	257.9
122.5°	297.4	287.5	281.6	278.6
125°	317.1	305.3	299.4	296.4
127.5°	335.9	323.1	315.2	311.2
130°	351.7	337.9	328.0	324.1
132.5°	366.5	351.7	340.8	335.9
135°	378.4	363.6	351.7	347.8
137.5°	391.2	375.4	363.6	358.6
140°	403.1	387.3	375.4	371.5
142.5°	414.0	398.1	387.3	384.3
145°	425.8	411.0	401.1	397.2
147.5°	437.7	423.8	414.0	411.0
150°	448.5	435.7	427.8	424.8
152.5°	458.4	447.5	439.6	438.7
155°	469.3	458.4	452.5	451.5
157.5°	478.2	468.3	463.4	462.4
160°	486.1	478.2	474.2	473.2
162.5°	493.0	487.1	483.1	484.1
165°	498.9	493.0	491.0	492.0
167.5°	503.9	499.9	497.9	498.9
170°	507.8	504.8	503.9	505.8
172.5°	510.8	507.8	508.8	509.8
175°	512.8	510.8	511.8	512.8
177.5°	513.7	511.8	512.8	514.7
180°	513.7	513.7	513.7	513.7

(END OF REPORT)