

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009933

Luminaire Tested: S122RDIP-B290D925UB35-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009933
REPORT IS A COMBINATION OF REPORTS P988201 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B290D925UB35-4F0-XX-W2A-A1
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4395.0 lumens
Efficiency: N/A
Efficacy: 105.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009933

CATALOG NUMBER: S122RDIP-B290D925UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1009933

CATALOG NUMBER: S122RDIP-B290D925UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33
1	93	89	85	82	82	79	76	73	61	59	58	45	44	43	30	29	29
2	85	78	72	67	75	70	65	61	54	51	48	40	38	36	27	26	25
3	77	69	62	57	69	62	56	51	48	44	41	36	33	31	24	23	22
4	71	61	54	48	63	55	49	44	43	39	35	32	29	27	22	20	19
5	65	54	47	41	58	49	42	38	39	34	31	29	26	24	20	18	17
6	60	49	41	36	53	44	38	33	35	30	27	26	23	21	18	16	15
7	56	44	37	31	49	40	33	29	32	27	24	24	21	19	17	15	14
8	52	40	33	28	46	36	30	26	29	24	21	22	19	17	16	14	12
9	48	36	29	25	43	33	27	23	26	22	19	20	17	15	14	13	11
10	45	33	27	22	40	30	24	20	24	20	17	19	16	14	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10112	10112	10112	10112
5°	10136	10742	10171	8581
10°	10024	11353	10096	7086
15°	9806	11356	9972	5323
20°	9545	9388	9752	4391
25°	9228	5866	9428	3736
30°	8823	3755	9063	3216
35°	8330	2887	8599	2752
40°	7782	2427	8114	2407
45°	7194	2065	7495	2021
50°	6593	1755	6901	1749
55°	5926	1525	6246	1504
60°	5335	1162	5617	1149
65°	4781	874	5066	992
70°	4170	699	4500	808
75°	3524	536	3849	612
80°	2802	364	3010	402
85°	1949	188	2133	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 9250 cd/sqm

TEST NUMBER: P1009933

CATALOG NUMBER: S122RDIP-B290D925UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.6	1.4
10°-20°	169.1	3.8
20°-30°	217.7	5.0
30°-40°	206.5	4.7
40°-50°	177.0	4.0
50°-60°	134.8	3.1
60°-70°	85.0	1.9
70°-80°	42.4	1.0
80°-90°	14.3	0.3
90°-100°	72.7	1.7
100°-110°	231.3	5.3
110°-120°	395.7	9.0
120°-130°	520.4	11.8
130°-140°	584.1	13.3
140°-150°	572.8	13.0
150°-160°	480.5	10.9
160°-170°	318.7	7.3
170°-180°	111.4	2.5
0°-30°	447.4	10.2
0°-40°	653.9	14.9
0°-60°	965.7	22.0
0°-90°	1107.3	25.2
90°-120°	699.7	15.9
90°-150°	2377.1	54.1
90°-180°	3288.0	74.8
0°-180°	4395.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	639	639	639	639	639	
5°	639	711	642	568	639	61
15°	602	802	613	376	602	169
25°	534	428	546	273	534	245
35°	439	211	453	201	439	274
45°	329	146	343	143	329	254
55°	222	102	234	100	222	200
65°	134	53	142	60	134	133
75°	63	28	69	32	63	68
85°	14	8	15	8	14	16
90°	1	34	1	34	1	4
95°	52	62	52	62	52	58
105°	213	220	213	220	213	225
115°	397	397	397	397	397	393
125°	578	580	578	580	578	516
135°	747	756	747	756	747	577
145°	907	917	907	917	907	567
155°	1037	1045	1037	1045	1037	477
165°	1128	1129	1128	1129	1128	318
175°	1174	1170	1174	1170	1174	112
180°	1176	1176	1176	1176	1176	

TEST NUMBER: P1009933

CATALOG NUMBER: S122RDIP-B290D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	642.8	645.5	646.8	648.6	652.6	655.3	659.3	660.2	659.7	661.5	656.6
5°	639.3	645.1	650.4	654.8	661.9	666.4	671.3	677.0	678.4	685.0	681.0
7.5°	634.4	642.8	650.4	659.3	669.9	675.7	683.2	692.1	696.1	704.1	706.3
10°	626.4	638.4	651.3	660.6	675.2	685.5	692.6	706.8	716.1	728.1	726.3
12.5°	613.5	629.1	646.4	661.9	681.0	687.7	701.0	715.6	727.6	738.7	748.5
15°	602.4	620.2	639.3	658.4	680.1	692.6	705.9	725.0	737.8	757.4	765.8
17.5°	587.3	610.0	632.6	653.9	679.7	693.9	710.3	729.0	748.1	766.7	773.4
20°	571.8	596.2	620.6	649.5	678.8	692.6	709.4	732.5	751.2	765.8	765.8
22.5°	553.2	582.9	610.9	638.4	670.4	690.3	707.7	734.7	748.1	751.2	739.2
25°	534.5	564.3	594.9	629.1	665.5	683.2	702.8	728.1	732.5	720.1	689.0
27.5°	512.3	545.6	580.2	617.1	655.3	677.5	695.2	712.1	703.7	670.4	622.0
30°	489.7	525.6	564.7	599.8	645.9	666.4	681.5	686.3	659.7	605.5	542.9
32.5°	466.1	501.2	542.5	584.7	631.3	650.8	660.6	647.7	598.9	530.5	454.2
35°	438.6	478.1	521.2	565.1	611.3	626.0	631.7	600.2	537.6	449.3	373.4
37.5°	413.8	453.3	499.4	544.3	589.1	597.1	591.3	542.1	462.6	375.1	301.0
40°	384.5	426.6	471.9	522.1	558.9	561.2	546.9	483.0	384.5	302.3	256.6
42.5°	357.4	400.0	445.3	496.3	524.3	516.8	497.7	413.8	321.0	260.6	223.8
45°	329.4	369.8	418.6	463.9	483.9	466.1	437.3	348.1	269.5	224.2	195.8
47.5°	302.3	340.1	388.5	432.0	435.5	415.5	381.4	291.7	233.5	197.1	174.0
50°	275.7	313.4	358.7	394.7	391.1	363.6	325.0	253.5	202.9	174.0	154.9
52.5°	249.1	283.2	327.2	355.6	340.5	313.9	275.7	214.9	177.1	151.8	137.2
55°	222.4	254.4	292.1	315.6	291.7	261.0	234.0	184.2	153.6	133.2	122.1
57.5°	200.2	225.5	260.2	274.4	245.5	221.5	198.0	158.5	133.2	118.5	105.7
60°	175.8	198.9	227.3	235.7	206.0	186.5	166.5	134.1	114.1	101.2	92.8
62.5°	154.9	174.0	195.8	195.8	169.6	154.9	139.8	112.3	95.9	85.7	81.7
65°	134.5	148.3	163.8	162.0	139.8	127.0	115.0	92.8	80.4	73.3	69.3
67.5°	114.5	125.2	135.4	129.2	113.2	102.1	91.0	75.0	66.6	61.7	56.4
70°	96.3	104.8	110.1	104.3	88.3	79.0	71.0	60.4	53.7	47.5	44.4
72.5°	80.8	84.4	86.1	79.0	65.7	60.4	54.6	47.1	41.3	38.2	37.3
75°	63.0	66.1	64.8	59.5	48.4	44.4	40.0	34.6	33.3	31.5	30.6
77.5°	49.3	49.3	47.1	42.2	34.6	31.5	29.7	27.1	25.7	25.3	24.4
80°	35.1	34.6	33.3	28.0	23.5	21.8	21.8	20.0	19.5	18.6	18.6
82.5°	23.1	23.1	21.3	16.9	15.5	15.1	14.7	13.8	13.8	13.3	13.3
85°	13.8	12.9	10.7	9.3	8.9	8.9	8.4	8.0	8.4	8.0	8.0
87.5°	6.2	4.9	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
90°	1.0	3.6	6.3	8.9	11.6	12.9	15.3	20.2	25.0	29.9	34.7
92.5°	21.8	23.6	25.4	27.1	28.9	29.8	29.9	30.1	30.4	30.6	30.8
95°	51.6	53.8	56.0	58.2	60.4	61.5	61.7	62.2	62.6	63.1	63.5
97.5°	86.3	88.3	90.3	92.3	94.3	95.3	95.7	96.6	97.5	98.3	99.2
100°	126.0	127.8	129.6	131.3	133.1	134.0	134.3	135.0	135.6	136.3	136.9
102.5°	167.7	169.0	170.4	171.7	173.0	173.7	174.1	175.0	175.9	176.7	177.6
105°	213.4	214.0	214.7	215.3	216.0	216.3	216.5	217.0	217.4	217.9	218.3
107.5°	259.0	259.9	260.8	261.7	262.6	263.0	263.0	263.0	263.0	263.0	263.0
110°	302.7	304.0	305.3	306.6	307.9	308.6	308.6	308.6	308.6	308.6	308.6



TEST NUMBER: P1009933

CATALOG NUMBER: S122RDIP-B290D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	350.3	351.6	352.9	354.2	355.5	356.2	356.1	355.9	355.7	355.5	355.3
115°	396.9	398.2	399.6	400.9	402.2	402.9	402.7	402.2	401.8	401.3	400.9
117.5°	443.6	445.4	447.1	448.9	450.6	451.5	451.0	449.9	448.8	447.7	446.6
120°	490.2	492.0	493.8	495.5	497.3	498.2	497.3	495.5	493.8	492.0	490.2
122.5°	532.9	535.1	537.3	539.5	541.7	542.8	542.2	541.1	540.0	538.9	537.8
125°	577.5	579.5	581.5	583.5	585.5	586.5	586.2	585.5	584.8	584.2	583.5
127.5°	621.2	623.6	626.0	628.5	630.9	632.1	631.7	630.8	629.9	629.1	628.2
130°	661.9	664.8	667.6	670.5	673.4	674.8	674.6	674.1	673.7	673.2	672.8
132.5°	707.5	709.7	711.9	714.2	716.4	717.5	717.6	717.8	718.1	718.3	718.5
135°	747.2	749.6	752.0	754.5	756.9	758.1	758.3	758.8	759.2	759.7	760.1
137.5°	790.9	792.9	794.9	796.8	798.8	799.8	800.0	800.5	800.9	801.4	801.8
140°	829.6	831.6	833.6	835.5	837.5	838.5	839.1	840.2	841.3	842.4	843.5
142.5°	869.3	871.3	873.3	875.2	877.2	878.2	878.5	879.2	879.9	880.5	881.2
145°	907.0	908.5	910.1	911.6	913.1	913.9	914.6	915.9	917.2	918.6	919.9
147.5°	940.7	942.7	944.7	946.7	948.7	949.7	950.1	951.0	951.9	952.7	953.6
150°	975.5	976.8	978.1	979.4	980.7	981.4	981.8	982.7	983.6	984.5	985.4
152.5°	1006.2	1007.5	1008.9	1010.2	1011.5	1012.2	1012.7	1013.8	1014.9	1016.0	1017.1
155°	1037.0	1037.7	1038.3	1039.0	1039.7	1040.0	1040.3	1041.0	1041.6	1042.3	1042.9
157.5°	1063.8	1064.2	1064.7	1065.1	1065.6	1065.8	1066.0	1066.5	1066.9	1067.4	1067.8
160°	1087.6	1088.0	1088.5	1088.9	1089.4	1089.6	1089.7	1089.9	1090.2	1090.4	1090.6
162.5°	1109.4	1109.4	1109.4	1109.4	1109.4	1109.4	1109.5	1109.7	1110.0	1110.2	1110.4
165°	1128.3	1128.1	1127.9	1127.6	1127.4	1127.3	1127.3	1127.3	1127.3	1127.3	1127.3
167.5°	1145.2	1144.5	1143.9	1143.2	1142.5	1142.2	1142.2	1142.2	1142.2	1142.2	1142.2
170°	1158.1	1157.4	1156.8	1156.1	1155.4	1155.1	1155.0	1154.8	1154.5	1154.3	1154.1
172.5°	1167.0	1166.3	1165.7	1165.0	1164.3	1164.0	1163.9	1163.7	1163.4	1163.2	1163.0
175°	1173.9	1173.3	1172.6	1172.0	1171.3	1171.0	1170.8	1170.3	1169.9	1169.4	1169.0
177.5°	1177.9	1177.2	1176.6	1175.9	1175.2	1174.9	1174.7	1174.2	1173.8	1173.3	1172.9
180°	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9

TEST NUMBER: P1009933

CATALOG NUMBER: S122RDIP-B290D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	661.5	662.4	663.7	669.9	670.8	672.6	671.7	671.7	672.1	671.3	671.7
5°	689.9	691.2	697.9	705.4	707.2	705.4	707.7	710.8	710.8	710.8	709.9
7.5°	716.5	721.4	729.0	740.1	742.3	744.5	748.5	745.8	746.7	750.7	749.4
10°	742.3	749.4	757.8	767.1	772.0	775.1	776.9	780.9	790.2	779.6	783.6
12.5°	766.7	776.9	785.8	796.0	799.6	803.5	804.9	808.4	808.4	808.0	811.1
15°	782.7	792.0	800.0	806.7	807.5	806.7	805.8	806.2	807.5	802.2	805.3
17.5°	786.2	787.1	789.8	787.1	787.6	778.2	772.9	771.6	759.2	759.6	769.8
20°	768.9	753.8	749.8	735.2	726.3	702.3	701.4	694.8	668.6	676.6	674.8
22.5°	721.4	695.7	661.5	644.6	636.2	610.9	591.3	577.6	568.3	558.9	554.9
25°	658.8	617.1	568.7	535.4	530.5	507.0	471.0	454.2	434.2	428.0	438.6
27.5°	578.0	523.9	469.3	418.2	408.9	387.6	369.4	357.4	334.3	333.0	333.8
30°	468.4	413.8	368.0	334.7	311.7	301.9	289.9	281.0	271.7	275.2	276.1
32.5°	384.9	333.0	290.3	272.6	261.9	255.7	245.5	239.7	235.7	234.4	234.0
35°	305.9	271.3	252.2	234.8	228.6	224.2	216.6	214.0	210.4	210.9	210.9
37.5°	261.9	233.1	218.9	210.0	204.2	202.0	197.1	194.4	192.2	191.3	192.7
40°	226.0	206.0	197.1	189.1	184.2	183.4	180.7	177.6	174.9	175.4	176.7
42.5°	199.8	188.2	177.6	171.4	167.8	166.5	164.3	162.0	162.0	160.7	160.3
45°	178.9	169.6	160.7	154.9	152.7	150.9	148.3	147.8	146.1	146.5	146.9
47.5°	160.3	152.7	146.1	140.3	138.1	137.6	135.0	133.2	133.2	132.7	132.3
50°	143.4	135.8	130.1	127.0	123.9	123.0	122.5	122.1	121.2	121.2	121.6
52.5°	129.6	122.1	117.6	115.0	113.2	112.3	112.3	111.9	111.9	111.9	111.4
55°	114.5	108.3	104.8	103.9	103.0	102.6	102.1	101.2	100.8	101.7	100.8
57.5°	100.3	98.1	95.0	94.1	91.9	91.9	90.6	89.7	88.8	89.7	89.7
60°	89.2	86.1	84.4	81.7	79.9	78.1	75.9	75.5	74.6	74.1	73.7
62.5°	77.7	75.0	70.6	66.6	63.9	62.2	61.3	60.8	60.8	60.4	60.4
65°	64.8	58.6	56.4	55.0	54.6	54.2	53.3	52.8	53.3	52.8	53.3
67.5°	50.6	49.7	48.4	47.5	47.1	46.6	46.6	46.2	46.2	46.2	46.2
70°	44.0	41.7	41.3	40.4	40.4	40.0	40.0	40.0	40.0	39.5	40.4
72.5°	36.4	35.1	34.6	34.2	34.2	34.2	33.7	33.7	33.7	33.3	33.7
75°	29.7	29.3	28.4	28.4	28.0	28.4	28.0	28.0	27.5	28.0	28.0
77.5°	24.0	23.5	23.1	23.1	22.6	22.6	22.6	22.6	22.6	22.6	23.1
80°	18.2	17.8	17.3	17.8	17.3	17.8	17.3	17.3	17.8	17.3	17.3
82.5°	13.3	12.9	12.9	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4
85°	8.0	7.5	7.5	8.0	7.5	8.0	7.5	7.5	7.5	8.0	8.0
87.5°	3.6	4.0	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	4.0
90°	34.3	33.8	33.4	32.9	32.7	32.8	33.0	33.3	33.5	33.7	33.5
92.5°	31.0	31.2	31.5	31.7	31.8	31.8	31.8	31.8	31.8	31.8	31.8
95°	63.5	63.5	63.5	63.5	63.5	63.3	62.8	62.4	61.9	61.5	61.9
97.5°	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2
100°	136.9	136.9	136.9	136.9	136.9	136.8	136.6	136.4	136.2	136.0	136.2
102.5°	177.8	178.0	178.3	178.5	178.6	178.5	178.3	178.0	177.8	177.6	177.8
105°	218.7	219.2	219.6	220.1	220.3	220.3	220.3	220.3	220.3	220.3	220.3
107.5°	263.2	263.4	263.7	263.9	264.0	263.4	262.3	261.2	260.1	259.0	260.1
110°	308.6	308.6	308.6	308.6	308.6	308.3	307.6	306.9	306.3	305.6	306.3

TEST NUMBER: P1009933

CATALOG NUMBER: S122RDIP-B290D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	354.6	354.0	353.3	352.6	352.3	352.1	351.6	351.2	350.7	350.3	350.7
115°	400.7	400.5	400.2	400.0	399.9	399.6	398.9	398.2	397.6	396.9	397.6
117.5°	445.9	445.3	444.6	443.9	443.6	443.3	442.6	441.9	441.3	440.6	441.3
120°	490.2	490.2	490.2	490.2	490.2	489.9	489.2	488.5	487.9	487.2	487.9
122.5°	537.2	536.5	535.9	535.2	534.9	534.7	534.2	533.8	533.3	532.9	533.3
125°	582.8	582.2	581.5	580.8	580.5	580.4	580.2	579.9	579.7	579.5	579.7
127.5°	627.3	626.4	625.5	624.6	624.2	623.9	623.2	622.5	621.9	621.2	621.9
130°	672.4	671.9	671.5	671.0	670.8	670.4	669.5	668.6	667.8	666.9	667.8
132.5°	717.4	716.3	715.2	714.1	713.5	713.2	712.5	711.8	711.2	710.5	711.2
135°	759.9	759.7	759.4	759.2	759.1	758.8	758.1	757.5	756.8	756.2	756.8
137.5°	801.6	801.4	801.1	800.9	800.8	800.4	799.5	798.6	797.7	796.8	797.7
140°	843.5	843.5	843.5	843.5	843.5	843.1	842.2	841.3	840.4	839.5	840.4
142.5°	881.4	881.6	881.9	882.1	882.2	881.8	880.9	880.0	879.1	878.2	879.1
145°	920.1	920.3	920.6	920.8	920.9	920.5	919.6	918.7	917.8	916.9	917.8
147.5°	954.0	954.5	954.9	955.4	955.6	955.2	954.3	953.4	952.6	951.7	952.6
150°	986.1	986.7	987.4	988.1	988.4	988.1	987.4	986.7	986.1	985.4	986.1
152.5°	1018.0	1018.9	1019.8	1020.7	1021.1	1020.7	1019.8	1018.9	1018.0	1017.1	1018.0
155°	1044.0	1045.1	1046.2	1047.3	1047.9	1047.6	1046.9	1046.2	1045.6	1044.9	1045.6
157.5°	1069.3	1070.9	1072.4	1073.9	1074.7	1074.1	1073.0	1071.9	1070.8	1069.7	1070.8
160°	1091.9	1093.2	1094.5	1095.8	1096.5	1096.1	1095.2	1094.3	1093.5	1092.6	1093.5
162.5°	1112.0	1113.5	1115.1	1116.6	1117.4	1116.8	1115.7	1114.6	1113.5	1112.4	1113.5
165°	1128.8	1130.4	1131.9	1133.4	1134.2	1133.7	1132.6	1131.5	1130.4	1129.3	1130.4
167.5°	1143.7	1145.3	1146.8	1148.3	1149.1	1148.6	1147.5	1146.4	1145.3	1144.2	1145.3
170°	1155.6	1157.2	1158.7	1160.2	1161.0	1160.3	1159.0	1157.7	1156.4	1155.1	1156.4
172.5°	1164.6	1166.1	1167.7	1169.2	1170.0	1169.3	1168.0	1166.7	1165.3	1164.0	1165.3
175°	1170.5	1172.1	1173.6	1175.1	1175.9	1175.2	1173.9	1172.6	1171.3	1170.0	1171.3
177.5°	1174.2	1175.6	1176.9	1178.2	1178.9	1178.2	1176.9	1175.6	1174.2	1172.9	1174.2
180°	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9

TEST NUMBER: P1009933

CATALOG NUMBER: S122RDIP-B290D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	673.5	670.4	669.5	670.4	669.5	669.9	666.8	655.3	658.4	653.5	656.2
5°	711.7	709.0	703.2	702.3	701.4	700.6	696.1	685.9	681.9	675.2	674.8
7.5°	748.1	748.1	743.6	740.5	736.5	733.4	727.6	712.5	706.3	698.3	693.9
10°	784.0	772.5	777.4	774.2	764.5	762.7	752.1	743.2	731.2	723.2	716.1
12.5°	809.8	806.2	801.8	799.1	796.4	790.7	783.6	760.9	754.7	738.7	730.7
15°	808.9	806.7	808.0	808.0	807.1	805.8	800.0	783.6	772.9	757.4	743.6
17.5°	765.4	771.1	776.9	780.9	789.8	793.8	799.1	789.3	782.7	769.4	754.7
20°	689.5	703.7	720.5	724.1	732.1	755.6	766.3	774.7	777.4	772.9	760.9
22.5°	583.8	595.8	636.6	635.7	647.3	675.2	706.3	731.6	751.6	762.7	758.3
25°	457.3	474.1	495.9	512.3	550.1	591.8	630.4	670.8	705.4	736.1	743.6
27.5°	345.8	368.0	385.3	407.1	426.2	475.5	525.2	588.2	628.6	686.8	717.0
30°	279.7	289.9	307.2	317.4	326.7	364.5	420.9	483.0	554.0	621.1	673.0
32.5°	238.8	245.9	258.8	263.3	273.0	298.3	333.8	390.7	463.9	545.2	613.5
35°	214.4	222.0	224.6	228.6	236.6	252.6	277.0	318.3	384.5	463.9	545.6
37.5°	193.6	197.6	205.1	207.8	210.4	222.4	238.8	267.7	311.7	376.9	467.5
40°	178.9	181.1	185.1	187.3	189.1	197.6	212.2	231.7	264.1	313.9	397.3
42.5°	163.4	166.0	168.7	171.4	173.6	180.2	189.1	207.8	229.5	267.3	327.6
45°	148.3	150.1	153.2	154.9	158.0	163.4	171.4	184.2	203.8	227.7	276.6
47.5°	134.5	136.7	138.1	140.3	142.5	148.3	155.8	164.3	180.2	203.8	239.3
50°	122.1	124.7	126.5	127.0	128.7	134.1	140.3	149.6	159.8	178.0	209.1
52.5°	113.2	113.7	115.0	116.8	116.3	119.4	125.2	132.3	143.0	157.6	180.2
55°	103.0	104.3	105.2	105.7	105.7	108.3	111.4	118.1	126.5	138.5	157.6
57.5°	90.1	91.5	94.1	95.0	96.3	97.7	99.0	103.4	110.5	122.1	137.6
60°	76.8	77.7	80.4	82.1	83.0	86.6	88.3	91.9	95.9	104.3	119.0
62.5°	61.7	62.6	63.9	65.7	67.5	72.8	77.2	80.8	83.9	89.7	101.7
65°	53.7	54.2	55.0	55.5	55.9	58.2	62.2	67.0	72.8	77.2	84.4
67.5°	46.6	47.1	47.5	48.4	48.8	49.3	51.1	52.4	58.2	64.4	69.7
70°	40.0	40.8	41.3	41.3	41.7	42.6	43.5	45.3	47.1	50.2	56.8
72.5°	33.7	34.2	35.1	35.1	35.1	36.0	36.8	37.7	38.6	40.4	43.1
75°	28.0	28.9	28.9	28.9	29.3	29.3	30.2	31.1	32.0	33.3	34.2
77.5°	23.1	23.1	23.1	23.1	23.5	23.5	24.0	24.9	25.3	25.7	26.6
80°	17.3	17.8	17.8	17.8	18.2	18.2	18.2	19.1	19.5	19.5	20.4
82.5°	12.9	12.9	12.9	13.3	12.9	13.3	13.3	13.8	13.3	13.8	14.2
85°	8.0	8.0	8.0	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.9
87.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.4	4.0	4.0
90°	33.3	33.0	32.8	32.7	32.9	33.4	33.8	34.3	34.7	29.9	25.0
92.5°	31.8	31.8	31.8	31.8	31.7	31.5	31.2	31.0	30.8	30.6	30.4
95°	62.4	62.8	63.3	63.5	63.5	63.5	63.5	63.5	63.5	63.1	62.6
97.5°	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	98.3	97.5
100°	136.4	136.6	136.8	136.9	136.9	136.9	136.9	136.9	136.9	136.3	135.6
102.5°	178.0	178.3	178.5	178.6	178.5	178.3	178.0	177.8	177.6	176.7	175.9
105°	220.3	220.3	220.3	220.3	220.1	219.6	219.2	218.7	218.3	217.9	217.4
107.5°	261.2	262.3	263.4	264.0	263.9	263.7	263.4	263.2	263.0	263.0	263.0
110°	306.9	307.6	308.3	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6

TEST NUMBER: P1009933

CATALOG NUMBER: S122RDIP-B290D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	351.2	351.6	352.1	352.3	352.6	353.3	354.0	354.6	355.3	355.5	355.7
115°	398.2	398.9	399.6	399.9	400.0	400.2	400.5	400.7	400.9	401.3	401.8
117.5°	441.9	442.6	443.3	443.6	443.9	444.6	445.3	445.9	446.6	447.7	448.8
120°	488.5	489.2	489.9	490.2	490.2	490.2	490.2	490.2	490.2	492.0	493.8
122.5°	533.8	534.2	534.7	534.9	535.2	535.9	536.5	537.2	537.8	538.9	540.0
125°	579.9	580.2	580.4	580.5	580.8	581.5	582.2	582.8	583.5	584.2	584.8
127.5°	622.5	623.2	623.9	624.2	624.6	625.5	626.4	627.3	628.2	629.1	629.9
130°	668.6	669.5	670.4	670.8	671.0	671.5	671.9	672.4	672.8	673.2	673.7
132.5°	711.8	712.5	713.2	713.5	714.1	715.2	716.3	717.4	718.5	718.3	718.1
135°	757.5	758.1	758.8	759.1	759.2	759.4	759.7	759.9	760.1	759.7	759.2
137.5°	798.6	799.5	800.4	800.8	800.9	801.1	801.4	801.6	801.8	801.4	800.9
140°	841.3	842.2	843.1	843.5	843.5	843.5	843.5	843.5	843.5	842.4	841.3
142.5°	880.0	880.9	881.8	882.2	882.1	881.9	881.6	881.4	881.2	880.5	879.9
145°	918.7	919.6	920.5	920.9	920.8	920.6	920.3	920.1	919.9	918.6	917.2
147.5°	953.4	954.3	955.2	955.6	955.4	954.9	954.5	954.0	953.6	952.7	951.9
150°	986.7	987.4	988.1	988.4	988.1	987.4	986.7	986.1	985.4	984.5	983.6
152.5°	1018.9	1019.8	1020.7	1021.1	1020.7	1019.8	1018.9	1018.0	1017.1	1016.0	1014.9
155°	1046.2	1046.9	1047.6	1047.9	1047.3	1046.2	1045.1	1044.0	1042.9	1042.3	1041.6
157.5°	1071.9	1073.0	1074.1	1074.7	1073.9	1072.4	1070.9	1069.3	1067.8	1067.4	1066.9
160°	1094.3	1095.2	1096.1	1096.5	1095.8	1094.5	1093.2	1091.9	1090.6	1090.4	1090.2
162.5°	1114.6	1115.7	1116.8	1117.4	1116.6	1115.1	1113.5	1112.0	1110.4	1110.2	1110.0
165°	1131.5	1132.6	1133.7	1134.2	1133.4	1131.9	1130.4	1128.8	1127.3	1127.3	1127.3
167.5°	1146.4	1147.5	1148.6	1149.1	1148.3	1146.8	1145.3	1143.7	1142.2	1142.2	1142.2
170°	1157.7	1159.0	1160.3	1161.0	1160.2	1158.7	1157.2	1155.6	1154.1	1154.3	1154.5
172.5°	1166.7	1168.0	1169.3	1170.0	1169.2	1167.7	1166.1	1164.6	1163.0	1163.2	1163.4
175°	1172.6	1173.9	1175.2	1175.9	1175.1	1173.6	1172.1	1170.5	1169.0	1169.4	1169.9
177.5°	1175.6	1176.9	1178.2	1178.9	1178.2	1176.9	1175.6	1174.2	1172.9	1173.3	1173.8
180°	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9

TEST NUMBER: P1009933

CATALOG NUMBER: S122RDIP-B290D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	652.2	649.9	649.9	648.6	648.6	641.5	641.5	643.7	641.1	638.0	633.5
5°	669.0	664.1	662.8	661.0	655.3	646.4	642.8	641.5	636.2	629.5	622.0
7.5°	685.0	677.0	673.0	669.0	661.5	649.1	642.0	637.1	629.1	618.9	609.1
10°	700.6	690.3	680.1	675.2	664.6	649.1	638.8	630.9	619.3	605.5	591.8
12.5°	714.8	693.4	691.7	681.9	666.4	648.6	633.1	621.5	606.9	590.9	574.9
15°	727.2	705.4	694.8	685.9	665.5	643.3	626.9	612.6	593.1	574.9	555.4
17.5°	733.4	709.9	702.8	688.1	667.3	638.4	616.2	598.9	577.6	555.8	533.6
20°	739.6	712.1	700.6	690.3	661.9	629.1	604.2	584.2	560.7	535.0	510.5
22.5°	742.7	712.1	698.3	684.1	656.6	618.9	589.6	566.0	538.5	512.3	483.0
25°	737.4	709.4	693.0	678.4	647.3	606.4	572.7	546.1	516.8	487.0	457.3
27.5°	724.1	703.2	684.1	669.0	634.4	590.5	554.9	524.7	494.6	461.3	431.1
30°	699.2	689.9	674.8	657.9	620.2	576.2	534.1	503.0	469.7	436.4	404.9
32.5°	660.6	668.6	658.8	644.2	603.3	556.7	511.9	480.4	443.9	408.0	379.1
35°	613.5	642.0	636.6	626.4	585.6	535.8	491.0	452.8	416.4	380.0	351.2
37.5°	562.0	605.1	609.5	603.3	565.1	514.5	465.3	428.0	390.7	353.8	324.5
40°	491.5	557.6	571.8	574.5	543.8	488.8	437.3	400.9	364.0	328.1	292.6
42.5°	426.6	510.1	527.9	539.0	516.8	463.5	411.5	371.1	334.7	302.3	266.8
45°	365.8	452.8	481.7	495.9	486.1	434.6	380.9	343.2	309.9	280.1	245.9
47.5°	303.2	390.7	431.1	453.7	453.7	405.3	351.6	314.3	282.4	257.0	226.9
50°	261.5	334.3	376.0	405.8	413.8	375.6	325.0	288.6	258.4	230.9	207.8
52.5°	222.9	288.1	322.8	353.8	376.9	343.6	295.2	262.4	232.6	206.9	188.7
55°	192.7	241.5	273.0	307.2	333.0	311.2	266.4	234.4	208.7	187.3	171.8
57.5°	163.8	206.4	232.2	262.4	289.9	273.5	237.5	210.0	187.3	168.7	154.9
60°	139.4	174.0	194.0	217.5	251.7	240.2	210.4	185.1	166.9	150.1	138.5
62.5°	118.5	146.1	162.9	179.8	210.9	205.5	182.5	162.9	147.4	133.2	123.4
65°	97.2	119.9	133.2	147.8	172.7	174.9	156.3	142.5	128.3	115.9	107.0
67.5°	78.6	96.3	108.3	120.8	140.7	146.9	134.1	122.5	110.5	100.3	92.3
70°	63.5	75.9	84.8	94.6	111.0	118.5	111.9	103.9	94.1	85.7	78.6
72.5°	50.2	58.2	63.5	71.0	84.4	91.9	91.5	84.4	77.2	71.5	65.7
75°	36.8	43.1	47.5	52.4	63.0	70.1	71.9	68.8	61.7	57.3	52.8
77.5°	28.0	31.5	33.7	37.3	44.8	51.1	53.7	52.8	47.9	44.4	41.3
80°	21.3	22.2	23.1	24.4	30.6	36.4	38.2	37.7	35.1	33.7	30.2
82.5°	15.1	15.5	16.0	16.4	18.6	23.5	25.3	26.2	24.0	22.6	19.5
85°	8.9	9.3	9.3	10.2	10.7	12.0	15.1	15.1	14.7	12.9	12.4
87.5°	4.4	4.4	4.0	4.0	4.4	4.9	5.8	6.7	5.8	5.3	4.9
90°	20.2	15.3	12.9	11.6	8.9	6.3	3.6	1.0	3.6	6.3	8.9
92.5°	30.1	29.9	29.8	28.9	27.1	25.4	23.6	21.8	23.6	25.4	27.1
95°	62.2	61.7	61.5	60.4	58.2	56.0	53.8	51.6	53.8	56.0	58.2
97.5°	96.6	95.7	95.3	94.3	92.3	90.3	88.3	86.3	88.3	90.3	92.3
100°	135.0	134.3	134.0	133.1	131.3	129.6	127.8	126.0	127.8	129.6	131.3
102.5°	175.0	174.1	173.7	173.0	171.7	170.4	169.0	167.7	169.0	170.4	171.7
105°	217.0	216.5	216.3	216.0	215.3	214.7	214.0	213.4	214.0	214.7	215.3
107.5°	263.0	263.0	263.0	262.6	261.7	260.8	259.9	259.0	259.9	260.8	261.7
110°	308.6	308.6	308.6	307.9	306.6	305.3	304.0	302.7	304.0	305.3	306.6

TEST NUMBER: P1009933

CATALOG NUMBER: S122RDIP-B290D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	355.9	356.1	356.2	355.5	354.2	352.9	351.6	350.3	351.6	352.9	354.2
115°	402.2	402.7	402.9	402.2	400.9	399.6	398.2	396.9	398.2	399.6	400.9
117.5°	449.9	451.0	451.5	450.6	448.9	447.1	445.4	443.6	445.4	447.1	448.9
120°	495.5	497.3	498.2	497.3	495.5	493.8	492.0	490.2	492.0	493.8	495.5
122.5°	541.1	542.2	542.8	541.7	539.5	537.3	535.1	532.9	535.1	537.3	539.5
125°	585.5	586.2	586.5	585.5	583.5	581.5	579.5	577.5	579.5	581.5	583.5
127.5°	630.8	631.7	632.1	630.9	628.5	626.0	623.6	621.2	623.6	626.0	628.5
130°	674.1	674.6	674.8	673.4	670.5	667.6	664.8	661.9	664.8	667.6	670.5
132.5°	717.8	717.6	717.5	716.4	714.2	711.9	709.7	707.5	709.7	711.9	714.2
135°	758.8	758.3	758.1	756.9	754.5	752.0	749.6	747.2	749.6	752.0	754.5
137.5°	800.5	800.0	799.8	798.8	796.8	794.9	792.9	790.9	792.9	794.9	796.8
140°	840.2	839.1	838.5	837.5	835.5	833.6	831.6	829.6	831.6	833.6	835.5
142.5°	879.2	878.5	878.2	877.2	875.2	873.3	871.3	869.3	871.3	873.3	875.2
145°	915.9	914.6	913.9	913.1	911.6	910.1	908.5	907.0	908.5	910.1	911.6
147.5°	951.0	950.1	949.7	948.7	946.7	944.7	942.7	940.7	942.7	944.7	946.7
150°	982.7	981.8	981.4	980.7	979.4	978.1	976.8	975.5	976.8	978.1	979.4
152.5°	1013.8	1012.7	1012.2	1011.5	1010.2	1008.9	1007.5	1006.2	1007.5	1008.9	1010.2
155°	1041.0	1040.3	1040.0	1039.7	1039.0	1038.3	1037.7	1037.0	1037.7	1038.3	1039.0
157.5°	1066.5	1066.0	1065.8	1065.6	1065.1	1064.7	1064.2	1063.8	1064.2	1064.7	1065.1
160°	1089.9	1089.7	1089.6	1089.4	1088.9	1088.5	1088.0	1087.6	1088.0	1088.5	1088.9
162.5°	1109.7	1109.5	1109.4	1109.4	1109.4	1109.4	1109.4	1109.4	1109.4	1109.4	1109.4
165°	1127.3	1127.3	1127.3	1127.4	1127.6	1127.9	1128.1	1128.3	1128.1	1127.9	1127.6
167.5°	1142.2	1142.2	1142.2	1142.5	1143.2	1143.9	1144.5	1145.2	1144.5	1143.9	1143.2
170°	1154.8	1155.0	1155.1	1155.4	1156.1	1156.8	1157.4	1158.1	1157.4	1156.8	1156.1
172.5°	1163.7	1163.9	1164.0	1164.3	1165.0	1165.7	1166.3	1167.0	1166.3	1165.7	1165.0
175°	1170.3	1170.8	1171.0	1171.3	1172.0	1172.6	1173.3	1173.9	1173.3	1172.6	1172.0
177.5°	1174.2	1174.7	1174.9	1175.2	1175.9	1176.6	1177.2	1177.9	1177.2	1176.6	1175.9
180°	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9

TEST NUMBER: P1009933

CATALOG NUMBER: S122RDIP-B290D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	631.7	632.2	633.5	629.5	623.3	620.6	612.6	611.3	610.0	610.0	611.3
5°	617.5	615.8	616.2	608.7	599.8	594.4	583.3	585.1	579.4	575.8	576.7
7.5°	602.0	597.1	596.7	586.9	575.8	566.0	554.5	551.8	546.5	540.3	537.6
10°	582.5	578.9	572.3	561.2	546.9	539.0	523.4	514.1	512.8	503.4	499.9
12.5°	562.5	556.3	549.6	534.1	518.1	505.2	493.7	483.5	476.4	468.4	463.0
15°	539.4	531.9	524.3	507.9	489.2	476.4	459.0	443.9	423.1	406.7	397.3
17.5°	514.1	505.7	495.4	477.2	459.0	441.3	409.3	391.6	376.9	367.1	361.4
20°	487.9	478.6	468.4	450.2	418.6	387.6	369.8	356.0	347.2	337.4	330.3
22.5°	460.4	450.6	439.5	411.1	377.8	356.0	342.3	329.4	316.5	311.2	307.7
25°	434.6	425.7	411.5	372.9	346.7	326.7	311.2	302.8	296.1	289.0	282.4
27.5°	408.0	391.6	371.6	339.2	322.8	302.3	291.2	285.0	273.5	268.6	265.5
30°	376.0	357.8	338.7	315.6	296.6	282.4	272.1	261.9	255.3	250.4	245.1
32.5°	343.6	326.3	314.3	290.3	276.1	261.5	251.7	245.5	235.7	232.6	230.4
35°	315.6	301.0	290.3	270.8	257.5	244.2	237.1	227.7	221.5	215.8	212.2
37.5°	288.1	280.1	269.0	252.6	238.4	227.7	218.0	214.9	206.4	203.3	199.8
40°	269.0	257.0	247.7	233.5	221.5	210.0	203.8	196.7	190.9	186.0	184.7
42.5°	245.9	237.1	231.7	216.2	203.8	197.1	189.6	181.6	177.1	173.1	168.3
45°	228.6	220.6	213.1	200.7	189.6	181.1	174.5	169.1	161.6	159.8	152.3
47.5°	210.4	202.4	196.7	184.2	174.0	166.0	161.2	154.1	147.8	143.8	140.3
50°	192.2	185.6	180.2	169.6	160.7	152.3	145.6	138.5	135.8	129.2	127.0
52.5°	174.9	170.5	164.7	154.5	145.6	138.5	131.4	125.6	121.6	118.1	115.4
55°	160.3	153.2	150.5	139.4	131.9	124.3	118.1	114.5	109.7	107.4	105.2
57.5°	143.8	139.8	135.4	127.0	118.5	111.4	107.0	101.7	99.0	96.3	94.6
60°	129.6	123.9	120.3	113.2	105.7	99.0	95.0	91.0	87.5	85.2	81.7
62.5°	113.2	108.8	106.5	99.0	92.8	86.6	83.0	79.0	76.4	72.4	67.9
65°	99.0	95.4	92.8	86.6	80.8	75.0	71.5	66.6	63.0	60.8	60.4
67.5°	86.6	83.9	79.9	74.1	68.4	63.9	59.9	55.9	55.5	54.6	54.6
70°	72.8	70.1	67.9	61.7	56.8	51.9	51.1	49.7	48.4	47.9	47.1
72.5°	60.8	58.6	55.9	50.6	45.7	44.4	43.5	42.6	41.3	40.8	40.4
75°	49.3	46.2	44.4	39.5	38.2	37.3	36.4	35.1	34.2	33.7	32.9
77.5°	37.7	34.6	34.6	32.0	31.1	29.7	28.9	28.0	27.5	26.6	26.6
80°	26.6	26.6	25.7	24.4	23.1	22.6	21.3	20.9	20.4	20.9	20.0
82.5°	19.5	17.8	17.8	16.9	16.0	15.5	14.7	14.7	14.2	14.2	14.2
85°	11.1	11.1	10.7	9.8	9.3	9.3	8.9	8.9	8.4	8.4	8.0
87.5°	4.4	4.0	4.4	4.0	4.0	3.6	3.6	3.6	3.1	3.6	3.1
90°	11.6	12.9	15.3	20.2	25.0	29.9	34.7	34.3	33.8	33.4	32.9
92.5°	28.9	29.8	29.9	30.1	30.4	30.6	30.8	31.0	31.2	31.5	31.7
95°	60.4	61.5	61.7	62.2	62.6	63.1	63.5	63.5	63.5	63.5	63.5
97.5°	94.3	95.3	95.7	96.6	97.5	98.3	99.2	99.2	99.2	99.2	99.2
100°	133.1	134.0	134.3	135.0	135.6	136.3	136.9	136.9	136.9	136.9	136.9
102.5°	173.0	173.7	174.1	175.0	175.9	176.7	177.6	177.8	178.0	178.3	178.5
105°	216.0	216.3	216.5	217.0	217.4	217.9	218.3	218.7	219.2	219.6	220.1
107.5°	262.6	263.0	263.0	263.0	263.0	263.0	263.0	263.2	263.4	263.7	263.9
110°	307.9	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6

TEST NUMBER: P1009933

CATALOG NUMBER: S122RDIP-B290D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	355.5	356.2	356.1	355.9	355.7	355.5	355.3	354.6	354.0	353.3	352.6
115°	402.2	402.9	402.7	402.2	401.8	401.3	400.9	400.7	400.5	400.2	400.0
117.5°	450.6	451.5	451.0	449.9	448.8	447.7	446.6	445.9	445.3	444.6	443.9
120°	497.3	498.2	497.3	495.5	493.8	492.0	490.2	490.2	490.2	490.2	490.2
122.5°	541.7	542.8	542.2	541.1	540.0	538.9	537.8	537.2	536.5	535.9	535.2
125°	585.5	586.5	586.2	585.5	584.8	584.2	583.5	582.8	582.2	581.5	580.8
127.5°	630.9	632.1	631.7	630.8	629.9	629.1	628.2	627.3	626.4	625.5	624.6
130°	673.4	674.8	674.6	674.1	673.7	673.2	672.8	672.4	671.9	671.5	671.0
132.5°	716.4	717.5	717.6	717.8	718.1	718.3	718.5	717.4	716.3	715.2	714.1
135°	756.9	758.1	758.3	758.8	759.2	759.7	760.1	759.9	759.7	759.4	759.2
137.5°	798.8	799.8	800.0	800.5	800.9	801.4	801.8	801.6	801.4	801.1	800.9
140°	837.5	838.5	839.1	840.2	841.3	842.4	843.5	843.5	843.5	843.5	843.5
142.5°	877.2	878.2	878.5	879.2	879.9	880.5	881.2	881.4	881.6	881.9	882.1
145°	913.1	913.9	914.6	915.9	917.2	918.6	919.9	920.1	920.3	920.6	920.8
147.5°	948.7	949.7	950.1	951.0	951.9	952.7	953.6	954.0	954.5	954.9	955.4
150°	980.7	981.4	981.8	982.7	983.6	984.5	985.4	986.1	986.7	987.4	988.1
152.5°	1011.5	1012.2	1012.7	1013.8	1014.9	1016.0	1017.1	1018.0	1018.9	1019.8	1020.7
155°	1039.7	1040.0	1040.3	1041.0	1041.6	1042.3	1042.9	1044.0	1045.1	1046.2	1047.3
157.5°	1065.6	1065.8	1066.0	1066.5	1066.9	1067.4	1067.8	1069.3	1070.9	1072.4	1073.9
160°	1089.4	1089.6	1089.7	1089.9	1090.2	1090.4	1090.6	1091.9	1093.2	1094.5	1095.8
162.5°	1109.4	1109.4	1109.5	1109.7	1110.0	1110.2	1110.4	1112.0	1113.5	1115.1	1116.6
165°	1127.4	1127.3	1127.3	1127.3	1127.3	1127.3	1127.3	1128.8	1130.4	1131.9	1133.4
167.5°	1142.5	1142.2	1142.2	1142.2	1142.2	1142.2	1142.2	1143.7	1145.3	1146.8	1148.3
170°	1155.4	1155.1	1155.0	1154.8	1154.5	1154.3	1154.1	1155.6	1157.2	1158.7	1160.2
172.5°	1164.3	1164.0	1163.9	1163.7	1163.4	1163.2	1163.0	1164.6	1166.1	1167.7	1169.2
175°	1171.3	1171.0	1170.8	1170.3	1169.9	1169.4	1169.0	1170.5	1172.1	1173.6	1175.1
177.5°	1175.2	1174.9	1174.7	1174.2	1173.8	1173.3	1172.9	1174.2	1175.6	1176.9	1178.2
180°	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9

TEST NUMBER: P1009933

CATALOG NUMBER: S122RDIP-B290D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	611.3	610.4	607.8	608.7	607.3	607.3	606.4	606.4	606.4	608.7	607.3
5°	578.0	574.9	571.8	570.5	569.1	567.8	567.8	567.4	571.4	570.5	574.0
7.5°	536.7	535.8	529.6	529.6	527.4	526.5	528.7	529.2	529.6	530.5	532.7
10°	499.9	497.7	488.8	489.7	488.3	486.6	487.9	487.0	490.1	491.0	490.1
12.5°	456.4	452.4	442.6	437.7	432.4	428.4	433.3	429.7	442.2	445.7	455.5
15°	398.7	391.1	384.5	384.5	379.6	376.0	378.2	382.2	384.9	388.9	390.7
17.5°	360.0	356.9	351.6	348.5	347.2	345.8	345.8	347.6	353.4	352.9	356.5
20°	327.2	325.4	322.8	318.8	317.4	316.5	316.5	316.5	320.5	324.1	326.3
22.5°	304.5	303.2	301.4	296.1	293.5	292.6	294.8	296.1	299.2	301.9	304.1
25°	281.9	278.8	275.7	273.9	272.6	272.6	273.5	273.9	275.2	276.6	279.2
27.5°	263.3	261.0	256.6	251.7	251.7	250.4	251.3	252.2	255.3	259.7	261.9
30°	242.4	242.0	240.2	238.4	236.6	235.7	237.5	238.8	239.3	241.5	241.5
32.5°	227.3	224.2	221.1	219.3	218.4	218.0	218.4	220.2	220.2	222.9	226.0
35°	212.2	210.4	207.3	204.2	203.3	201.1	202.9	204.7	207.8	209.1	210.4
37.5°	195.8	193.6	192.2	191.3	189.6	190.0	188.7	191.3	194.0	193.6	194.4
40°	183.4	179.4	175.4	174.9	174.5	174.0	174.0	174.5	176.2	178.0	180.7
42.5°	167.4	166.0	162.5	158.9	158.0	157.2	156.3	158.0	161.6	164.7	166.0
45°	150.9	149.2	148.3	145.6	143.8	143.4	142.5	144.7	147.8	149.2	150.1
47.5°	135.8	135.4	132.7	133.2	131.9	132.3	131.9	133.2	133.2	134.5	135.4
50°	125.6	124.3	123.0	122.1	120.8	120.8	120.3	120.8	122.5	124.3	123.9
52.5°	115.4	113.2	112.8	112.3	111.4	112.3	111.0	111.4	113.2	114.1	113.7
55°	103.4	103.0	102.1	101.2	100.8	100.3	100.3	100.3	102.1	103.4	103.9
57.5°	94.1	91.9	90.1	90.1	88.3	87.9	88.8	89.2	90.6	91.5	92.3
60°	81.2	80.4	77.7	76.4	73.7	73.3	73.3	75.0	77.2	80.4	81.2
62.5°	67.5	66.1	65.7	65.7	65.7	65.7	65.7	65.7	65.7	66.1	66.1
65°	59.9	60.4	59.9	59.5	59.9	59.9	59.5	59.5	59.5	59.9	60.4
67.5°	53.7	53.3	53.7	53.3	52.8	52.8	52.4	52.8	53.3	53.7	53.7
70°	46.6	46.6	46.2	46.6	46.2	45.7	45.3	45.3	46.2	46.6	46.6
72.5°	40.0	40.0	39.5	39.5	38.6	38.6	39.1	38.6	38.6	40.0	40.0
75°	33.3	32.9	32.4	32.4	32.0	32.0	32.0	31.5	32.4	32.4	32.9
77.5°	26.2	26.2	26.2	25.7	25.7	25.3	25.3	25.7	25.7	25.7	26.2
80°	20.0	20.0	20.0	19.5	19.1	19.1	19.1	19.1	19.1	19.5	19.1
82.5°	13.8	13.8	13.8	13.8	13.8	13.3	13.3	13.3	13.8	13.8	13.3
85°	8.4	8.0	8.4	8.4	8.0	8.4	8.0	8.0	7.5	7.5	8.0
87.5°	3.6	3.1	2.7	2.7	3.1	2.7	2.7	2.7	3.1	2.7	2.7
90°	32.7	32.8	33.0	33.3	33.5	33.7	33.5	33.3	33.0	32.8	32.7
92.5°	31.8	31.8	31.8	31.8	31.8	31.8	31.8	31.8	31.8	31.8	31.8
95°	63.5	63.3	62.8	62.4	61.9	61.5	61.9	62.4	62.8	63.3	63.5
97.5°	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2
100°	136.9	136.8	136.6	136.4	136.2	136.0	136.2	136.4	136.6	136.8	136.9
102.5°	178.6	178.5	178.3	178.0	177.8	177.6	177.8	178.0	178.3	178.5	178.6
105°	220.3	220.3	220.3	220.3	220.3	220.3	220.3	220.3	220.3	220.3	220.3
107.5°	264.0	263.4	262.3	261.2	260.1	259.0	260.1	261.2	262.3	263.4	264.0
110°	308.6	308.3	307.6	306.9	306.3	305.6	306.3	306.9	307.6	308.3	308.6

TEST NUMBER: P1009933

CATALOG NUMBER: S122RDIP-B290D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	352.3	352.1	351.6	351.2	350.7	350.3	350.7	351.2	351.6	352.1	352.3
115°	399.9	399.6	398.9	398.2	397.6	396.9	397.6	398.2	398.9	399.6	399.9
117.5°	443.6	443.3	442.6	441.9	441.3	440.6	441.3	441.9	442.6	443.3	443.6
120°	490.2	489.9	489.2	488.5	487.9	487.2	487.9	488.5	489.2	489.9	490.2
122.5°	534.9	534.7	534.2	533.8	533.3	532.9	533.3	533.8	534.2	534.7	534.9
125°	580.5	580.4	580.2	579.9	579.7	579.5	579.7	579.9	580.2	580.4	580.5
127.5°	624.2	623.9	623.2	622.5	621.9	621.2	621.9	622.5	623.2	623.9	624.2
130°	670.8	670.4	669.5	668.6	667.8	666.9	667.8	668.6	669.5	670.4	670.8
132.5°	713.5	713.2	712.5	711.8	711.2	710.5	711.2	711.8	712.5	713.2	713.5
135°	759.1	758.8	758.1	757.5	756.8	756.2	756.8	757.5	758.1	758.8	759.1
137.5°	800.8	800.4	799.5	798.6	797.7	796.8	797.7	798.6	799.5	800.4	800.8
140°	843.5	843.1	842.2	841.3	840.4	839.5	840.4	841.3	842.2	843.1	843.5
142.5°	882.2	881.8	880.9	880.0	879.1	878.2	879.1	880.0	880.9	881.8	882.2
145°	920.9	920.5	919.6	918.7	917.8	916.9	917.8	918.7	919.6	920.5	920.9
147.5°	955.6	955.2	954.3	953.4	952.6	951.7	952.6	953.4	954.3	955.2	955.6
150°	988.4	988.1	987.4	986.7	986.1	985.4	986.1	986.7	987.4	988.1	988.4
152.5°	1021.1	1020.7	1019.8	1018.9	1018.0	1017.1	1018.0	1018.9	1019.8	1020.7	1021.1
155°	1047.9	1047.6	1046.9	1046.2	1045.6	1044.9	1045.6	1046.2	1046.9	1047.6	1047.9
157.5°	1074.7	1074.1	1073.0	1071.9	1070.8	1069.7	1070.8	1071.9	1073.0	1074.1	1074.7
160°	1096.5	1096.1	1095.2	1094.3	1093.5	1092.6	1093.5	1094.3	1095.2	1096.1	1096.5
162.5°	1117.4	1116.8	1115.7	1114.6	1113.5	1112.4	1113.5	1114.6	1115.7	1116.8	1117.4
165°	1134.2	1133.7	1132.6	1131.5	1130.4	1129.3	1130.4	1131.5	1132.6	1133.7	1134.2
167.5°	1149.1	1148.6	1147.5	1146.4	1145.3	1144.2	1145.3	1146.4	1147.5	1148.6	1149.1
170°	1161.0	1160.3	1159.0	1157.7	1156.4	1155.1	1156.4	1157.7	1159.0	1160.3	1161.0
172.5°	1170.0	1169.3	1168.0	1166.7	1165.3	1164.0	1165.3	1166.7	1168.0	1169.3	1170.0
175°	1175.9	1175.2	1173.9	1172.6	1171.3	1170.0	1171.3	1172.6	1173.9	1175.2	1175.9
177.5°	1178.9	1178.2	1176.9	1175.6	1174.2	1172.9	1174.2	1175.6	1176.9	1178.2	1178.9
180°	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9

TEST NUMBER: P1009933

CATALOG NUMBER: S122RDIP-B290D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	608.7	610.9	610.0	605.1	610.0	611.3	614.0	616.6	618.4	621.1	623.3
5°	570.5	574.9	577.6	574.9	583.8	585.1	591.3	594.9	600.2	604.7	608.2
7.5°	534.5	538.1	543.4	544.3	549.6	555.8	564.7	573.6	582.0	586.5	590.5
10°	495.9	502.1	510.1	508.3	516.3	526.1	535.4	549.6	556.7	564.7	571.8
12.5°	457.3	461.3	471.9	475.5	487.0	494.6	507.4	516.3	534.1	543.4	549.6
15°	389.8	406.2	419.5	435.5	450.6	464.8	476.4	492.3	507.9	515.0	525.2
17.5°	359.2	366.7	374.7	382.7	402.2	427.5	447.9	465.3	478.6	487.9	499.9
20°	327.2	334.7	343.6	351.2	363.2	381.4	406.7	436.4	452.4	462.2	473.7
22.5°	304.5	311.7	317.4	324.1	333.4	346.7	365.8	402.7	424.0	436.0	446.2
25°	280.1	289.0	295.2	300.1	307.7	322.3	337.8	358.7	396.9	406.2	420.4
27.5°	263.3	265.9	273.0	280.6	288.1	296.1	312.1	329.9	355.6	376.0	393.3
30°	243.3	249.9	256.6	259.7	266.4	277.9	287.7	306.8	326.7	342.7	363.6
32.5°	228.2	232.2	236.6	244.2	250.4	258.4	268.1	284.1	301.0	311.2	327.2
35°	211.3	214.0	223.3	226.4	232.6	240.6	250.4	262.8	281.0	289.0	300.6
37.5°	195.3	201.6	204.2	211.3	217.1	225.1	232.2	246.4	258.4	267.7	278.4
40°	182.9	185.6	190.5	196.7	201.6	207.8	216.6	226.9	239.7	247.3	256.6
42.5°	167.8	170.0	176.2	179.8	187.8	193.6	198.9	211.3	222.9	228.6	238.0
45°	151.4	156.7	160.7	167.8	172.3	179.4	186.0	194.9	205.5	212.2	217.5
47.5°	137.2	142.5	146.5	153.2	160.3	163.4	170.5	179.8	189.6	194.9	202.4
50°	125.6	127.4	135.0	138.1	145.6	151.8	156.7	164.7	175.4	178.5	184.7
52.5°	114.5	115.9	120.8	124.7	131.4	136.7	143.0	150.5	159.4	164.3	169.1
55°	104.8	105.7	107.9	112.3	116.8	123.4	129.2	136.3	143.8	149.2	153.6
57.5°	93.7	95.4	97.2	99.9	104.3	110.5	116.8	123.4	129.6	133.2	139.0
60°	80.8	83.5	86.6	89.7	92.8	97.2	104.3	110.5	116.3	119.4	123.9
62.5°	67.0	72.4	75.0	78.6	81.2	85.2	90.6	97.7	101.7	105.7	109.2
65°	60.4	60.8	61.3	64.8	69.7	73.7	78.6	83.9	90.1	92.8	95.4
67.5°	53.7	54.2	55.0	55.5	57.3	61.7	67.0	72.8	77.7	79.5	82.1
70°	47.1	47.1	48.8	49.3	49.7	50.2	54.6	60.4	64.8	67.0	70.1
72.5°	40.0	40.4	41.3	41.7	42.6	43.5	44.8	47.9	53.3	55.5	59.0
75°	32.9	33.3	33.7	34.2	35.5	36.0	37.3	39.1	41.3	44.0	46.2
77.5°	26.2	26.2	26.6	27.5	28.4	28.9	30.2	31.1	32.0	33.3	35.1
80°	19.5	20.0	20.0	20.9	20.9	21.3	21.8	23.1	24.0	24.9	25.7
82.5°	13.3	14.2	14.2	14.2	14.7	15.1	15.5	15.5	16.4	16.9	18.2
85°	8.0	8.4	8.4	8.4	8.0	8.9	8.9	9.3	9.3	9.3	9.8
87.5°	3.1	2.7	3.1	3.1	3.1	3.6	3.1	3.1	3.6	4.0	4.0
90°	32.9	33.4	33.8	34.3	34.7	29.9	25.0	20.2	15.3	12.9	11.6
92.5°	31.7	31.5	31.2	31.0	30.8	30.6	30.4	30.1	29.9	29.8	28.9
95°	63.5	63.5	63.5	63.5	63.5	63.1	62.6	62.2	61.7	61.5	60.4
97.5°	99.2	99.2	99.2	99.2	99.2	98.3	97.5	96.6	95.7	95.3	94.3
100°	136.9	136.9	136.9	136.9	136.9	136.3	135.6	135.0	134.3	134.0	133.1
102.5°	178.5	178.3	178.0	177.8	177.6	176.7	175.9	175.0	174.1	173.7	173.0
105°	220.1	219.6	219.2	218.7	218.3	217.9	217.4	217.0	216.5	216.3	216.0
107.5°	263.9	263.7	263.4	263.2	263.0	263.0	263.0	263.0	263.0	263.0	262.6
110°	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6	307.9

TEST NUMBER: P1009933

CATALOG NUMBER: S122RDIP-B290D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	352.6	353.3	354.0	354.6	355.3	355.5	355.7	355.9	356.1	356.2	355.5
115°	400.0	400.2	400.5	400.7	400.9	401.3	401.8	402.2	402.7	402.9	402.2
117.5°	443.9	444.6	445.3	445.9	446.6	447.7	448.8	449.9	451.0	451.5	450.6
120°	490.2	490.2	490.2	490.2	490.2	492.0	493.8	495.5	497.3	498.2	497.3
122.5°	535.2	535.9	536.5	537.2	537.8	538.9	540.0	541.1	542.2	542.8	541.7
125°	580.8	581.5	582.2	582.8	583.5	584.2	584.8	585.5	586.2	586.5	585.5
127.5°	624.6	625.5	626.4	627.3	628.2	629.1	629.9	630.8	631.7	632.1	630.9
130°	671.0	671.5	671.9	672.4	672.8	673.2	673.7	674.1	674.6	674.8	673.4
132.5°	714.1	715.2	716.3	717.4	718.5	718.3	718.1	717.8	717.6	717.5	716.4
135°	759.2	759.4	759.7	759.9	760.1	759.7	759.2	758.8	758.3	758.1	756.9
137.5°	800.9	801.1	801.4	801.6	801.8	801.4	800.9	800.5	800.0	799.8	798.8
140°	843.5	843.5	843.5	843.5	843.5	842.4	841.3	840.2	839.1	838.5	837.5
142.5°	882.1	881.9	881.6	881.4	881.2	880.5	879.9	879.2	878.5	878.2	877.2
145°	920.8	920.6	920.3	920.1	919.9	918.6	917.2	915.9	914.6	913.9	913.1
147.5°	955.4	954.9	954.5	954.0	953.6	952.7	951.9	951.0	950.1	949.7	948.7
150°	988.1	987.4	986.7	986.1	985.4	984.5	983.6	982.7	981.8	981.4	980.7
152.5°	1020.7	1019.8	1018.9	1018.0	1017.1	1016.0	1014.9	1013.8	1012.7	1012.2	1011.5
155°	1047.3	1046.2	1045.1	1044.0	1042.9	1042.3	1041.6	1041.0	1040.3	1040.0	1039.7
157.5°	1073.9	1072.4	1070.9	1069.3	1067.8	1067.4	1066.9	1066.5	1066.0	1065.8	1065.6
160°	1095.8	1094.5	1093.2	1091.9	1090.6	1090.4	1090.2	1089.9	1089.7	1089.6	1089.4
162.5°	1116.6	1115.1	1113.5	1112.0	1110.4	1110.2	1110.0	1109.7	1109.5	1109.4	1109.4
165°	1133.4	1131.9	1130.4	1128.8	1127.3	1127.3	1127.3	1127.3	1127.3	1127.3	1127.4
167.5°	1148.3	1146.8	1145.3	1143.7	1142.2	1142.2	1142.2	1142.2	1142.2	1142.2	1142.5
170°	1160.2	1158.7	1157.2	1155.6	1154.1	1154.3	1154.5	1154.8	1155.0	1155.1	1155.4
172.5°	1169.2	1167.7	1166.1	1164.6	1163.0	1163.2	1163.4	1163.7	1163.9	1164.0	1164.3
175°	1175.1	1173.6	1172.1	1170.5	1169.0	1169.4	1169.9	1170.3	1170.8	1171.0	1171.3
177.5°	1178.2	1176.9	1175.6	1174.2	1172.9	1173.3	1173.8	1174.2	1174.7	1174.9	1175.2
180°	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9

TEST NUMBER: P1009933

CATALOG NUMBER: S122RDIP-B290D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	638.8	638.8	638.8	638.8
2.5°	627.3	626.0	634.0	642.8
5°	614.4	616.6	626.9	639.3
7.5°	601.1	606.0	618.0	634.4
10°	582.5	591.3	609.5	626.4
12.5°	564.3	576.2	593.6	613.5
15°	543.8	557.2	578.5	602.4
17.5°	521.2	536.3	561.2	587.3
20°	497.2	517.2	543.4	571.8
22.5°	470.6	494.6	521.6	553.2
25°	444.8	471.0	498.1	534.5
27.5°	419.5	445.3	475.5	512.3
30°	394.2	417.8	450.2	489.7
32.5°	367.1	391.6	425.7	466.1
35°	342.3	366.7	398.7	438.6
37.5°	315.6	341.8	372.5	413.8
40°	284.6	315.2	344.9	384.5
42.5°	258.8	291.2	320.1	357.4
45°	238.4	269.0	293.0	329.4
47.5°	219.3	244.2	268.6	302.3
50°	201.1	220.2	245.5	275.7
52.5°	182.5	198.9	220.6	249.1
55°	165.6	181.1	200.7	222.4
57.5°	150.1	161.2	180.7	200.2
60°	132.7	144.3	159.4	175.8
62.5°	118.1	127.0	141.2	154.9
65°	102.6	111.0	121.6	134.5
67.5°	88.3	95.9	104.3	114.5
70°	75.5	81.2	87.5	96.3
72.5°	61.7	67.9	73.7	80.8
75°	50.6	53.3	58.2	63.0
77.5°	39.1	42.6	45.3	49.3
80°	28.0	31.1	32.0	35.1
82.5°	18.6	20.4	22.2	23.1
85°	10.7	11.5	13.3	13.8
87.5°	4.0	4.4	5.3	6.2
90°	8.9	6.3	3.6	1.0
92.5°	27.1	25.4	23.6	21.8
95°	58.2	56.0	53.8	51.6
97.5°	92.3	90.3	88.3	86.3
100°	131.3	129.6	127.8	126.0
102.5°	171.7	170.4	169.0	167.7
105°	215.3	214.7	214.0	213.4
107.5°	261.7	260.8	259.9	259.0
110°	306.6	305.3	304.0	302.7



TEST NUMBER: P1009933

CATALOG NUMBER: S122RDIP-B290D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	354.2	352.9	351.6	350.3
115°	400.9	399.6	398.2	396.9
117.5°	448.9	447.1	445.4	443.6
120°	495.5	493.8	492.0	490.2
122.5°	539.5	537.3	535.1	532.9
125°	583.5	581.5	579.5	577.5
127.5°	628.5	626.0	623.6	621.2
130°	670.5	667.6	664.8	661.9
132.5°	714.2	711.9	709.7	707.5
135°	754.5	752.0	749.6	747.2
137.5°	796.8	794.9	792.9	790.9
140°	835.5	833.6	831.6	829.6
142.5°	875.2	873.3	871.3	869.3
145°	911.6	910.1	908.5	907.0
147.5°	946.7	944.7	942.7	940.7
150°	979.4	978.1	976.8	975.5
152.5°	1010.2	1008.9	1007.5	1006.2
155°	1039.0	1038.3	1037.7	1037.0
157.5°	1065.1	1064.7	1064.2	1063.8
160°	1088.9	1088.5	1088.0	1087.6
162.5°	1109.4	1109.4	1109.4	1109.4
165°	1127.6	1127.9	1128.1	1128.3
167.5°	1143.2	1143.9	1144.5	1145.2
170°	1156.1	1156.8	1157.4	1158.1
172.5°	1165.0	1165.7	1166.3	1167.0
175°	1172.0	1172.6	1173.3	1173.9
177.5°	1175.9	1176.6	1177.2	1177.9
180°	1175.9	1175.9	1175.9	1175.9

(END OF REPORT)