

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009938

Luminaire Tested: S122RDIP-B290D925UB40-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009938
REPORT IS A COMBINATION OF REPORTS P988206 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B290D925UB40-4F0-XX-W2A-A
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4738.0 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009938

CATALOG NUMBER: S122RDIP-B290D925UB40-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1009938

CATALOG NUMBER: S122RDIP-B290D925UB40-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	31	31	23
1	92	88	84	81	82	78	75	73	60	58	57	44	42	41	28	28	27	27	27	20
2	84	77	72	67	75	69	64	60	53	50	47	39	37	35	25	24	23	23	23	17
3	77	68	61	56	68	61	55	51	47	43	40	35	32	30	23	21	20	20	20	15
4	70	61	53	48	62	54	48	43	42	38	35	31	28	26	21	19	18	18	18	13
5	65	54	46	41	57	48	42	37	38	33	30	28	25	23	19	17	16	16	16	12
6	60	48	41	35	53	43	37	32	34	30	26	25	22	20	17	15	14	14	14	11
7	55	44	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	13	13	10
8	51	40	32	27	45	36	29	25	28	24	20	21	18	16	15	13	11	11	11	9
9	48	36	29	24	42	33	27	22	26	21	18	19	17	14	14	12	10	10	10	8
10	44	33	26	22	40	30	24	20	24	19	16	18	15	13	13	11	10	10	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10012	10012	10012	10012
5°	10035	10634	10070	8496
10°	9925	11240	9995	7015
15°	9709	11243	9873	5270
20°	9450	9293	9655	4348
25°	9136	5807	9333	3699
30°	8735	3718	8973	3185
35°	8248	2858	8514	2725
40°	7703	2402	8033	2384
45°	7122	2044	7421	2001
50°	6526	1737	6832	1731
55°	5867	1510	6185	1489
60°	5283	1151	5562	1137
65°	4735	866	5016	982
70°	4131	692	4452	801
75°	3491	530	3810	605
80°	2770	359	2986	397
85°	1921	186	2105	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 9159 cd/sqm

TEST NUMBER: P1009938

CATALOG NUMBER: S122RDIP-B290D925UB40-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.0	1.3
10°-20°	167.5	3.5
20°-30°	215.5	4.5
30°-40°	204.5	4.3
40°-50°	175.2	3.7
50°-60°	133.4	2.8
60°-70°	84.2	1.8
70°-80°	42.0	0.9
80°-90°	13.0	0.3
90°-100°	41.0	0.9
100°-110°	152.7	3.2
110°-120°	405.1	8.5
120°-130°	671.9	14.2
130°-140°	713.7	15.1
140°-150°	663.3	14.0
150°-160°	533.3	11.3
160°-170°	343.6	7.3
170°-180°	118.3	2.5
0°-30°	443.0	9.3
0°-40°	647.4	13.7
0°-60°	956.1	20.2
0°-90°	1095.2	23.1
90°-120°	598.8	12.6
90°-150°	2647.7	55.9
90°-180°	3643.0	76.9
0°-180°	4738.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	632	632	632	632	632	
5°	633	704	635	562	633	60
15°	596	794	606	372	596	168
25°	529	424	541	270	529	243
35°	434	209	448	199	434	272
45°	326	145	340	142	326	252
55°	220	101	232	99	220	198
65°	133	52	141	59	133	132
75°	62	28	68	32	62	68
85°	14	8	15	8	14	15
90°	1	24	1	24	1	4
95°	58	39	58	39	58	69
105°	273	68	273	68	273	292
115°	517	74	517	74	517	509
125°	731	769	731	769	731	652
135°	904	934	904	934	904	699
145°	1049	1066	1049	1066	1049	656
155°	1155	1156	1155	1156	1155	532
165°	1217	1215	1217	1215	1217	344
175°	1245	1238	1245	1238	1245	119
180°	1243	1243	1243	1243	1243	

TEST NUMBER: P1009938

CATALOG NUMBER: S122RDIP-B290D925UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	636.4	639.1	640.4	642.1	646.1	648.7	652.7	653.6	653.1	654.9	650.1
5°	632.9	638.6	643.9	648.3	655.3	659.7	664.6	670.3	671.6	678.2	674.2
7.5°	628.1	636.4	643.9	652.7	663.2	669.0	676.4	685.2	689.2	697.1	699.3
10°	620.2	632.0	644.8	654.0	668.5	678.6	685.7	699.7	709.0	720.8	719.1
12.5°	607.4	622.8	639.9	655.3	674.2	680.8	694.0	708.5	720.4	731.4	741.0
15°	596.4	614.0	632.9	651.8	673.4	685.7	698.8	717.7	730.5	749.8	758.2
17.5°	581.5	603.9	626.3	647.4	672.9	687.0	703.2	721.7	740.6	759.1	765.7
20°	566.1	590.3	614.5	643.0	672.0	685.7	702.4	725.2	743.7	758.2	758.2
22.5°	547.6	577.1	604.8	632.0	663.7	683.5	700.6	727.4	740.6	743.7	731.8
25°	529.2	558.6	589.0	622.8	658.8	676.4	695.8	720.8	725.2	712.9	682.1
27.5°	507.2	540.2	574.5	610.9	648.7	670.7	688.3	705.0	696.6	663.7	615.8
30°	484.8	520.4	559.1	593.8	639.5	659.7	674.7	679.5	653.1	599.5	537.5
32.5°	461.5	496.2	537.1	578.9	625.0	644.3	654.0	641.3	592.9	525.2	449.6
35°	434.3	473.4	516.0	559.5	605.2	619.7	625.4	594.2	532.3	444.8	369.6
37.5°	409.6	448.8	494.5	538.9	583.3	591.2	585.4	536.7	458.0	371.4	298.0
40°	380.6	422.4	467.2	516.9	553.4	555.6	541.5	478.2	380.6	299.3	254.0
42.5°	353.8	396.0	440.8	491.4	519.1	511.6	492.7	409.6	317.8	258.0	221.5
45°	326.1	366.1	414.5	459.3	479.1	461.5	432.9	344.6	266.8	222.0	193.8
47.5°	299.3	336.7	384.6	427.7	431.2	411.4	377.6	288.8	231.2	195.1	172.3
50°	272.9	310.3	355.1	390.7	387.2	360.0	321.7	251.0	200.9	172.3	153.4
52.5°	246.6	280.4	323.9	352.1	337.1	310.7	272.9	212.7	175.4	150.3	135.8
55°	220.2	251.8	289.2	312.5	288.8	258.4	231.6	182.4	152.1	131.9	120.9
57.5°	198.2	223.3	257.6	271.6	243.1	219.3	196.0	156.9	131.9	117.4	104.6
60°	174.1	196.9	225.0	233.4	203.9	184.6	164.8	132.7	113.0	100.2	91.9
62.5°	153.4	172.3	193.8	193.8	167.9	153.4	138.5	111.2	94.9	84.8	80.9
65°	133.2	146.8	162.2	160.4	138.5	125.7	113.8	91.9	79.6	72.5	68.6
67.5°	113.4	123.9	134.1	127.9	112.1	101.1	90.1	74.3	65.9	61.1	55.8
70°	95.4	103.7	109.0	103.3	87.5	78.2	70.3	59.8	53.2	47.0	44.0
72.5°	80.0	83.5	85.3	78.2	65.0	59.8	54.1	46.6	40.9	37.8	36.9
75°	62.4	65.5	64.2	58.9	47.9	44.0	39.6	34.3	33.0	31.2	30.3
77.5°	48.8	48.8	46.6	41.8	34.3	31.2	29.4	26.8	25.5	25.1	24.2
80°	34.7	34.3	33.0	27.7	23.3	21.5	21.5	19.8	19.3	18.5	18.5
82.5°	22.9	22.9	21.1	16.7	15.4	14.9	14.5	13.6	13.6	13.2	13.2
85°	13.6	12.7	10.5	9.2	8.8	8.8	8.4	7.9	8.4	7.9	7.9
87.5°	6.2	4.8	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
90°	0.9	3.1	5.3	7.5	9.7	10.8	11.6	13.2	14.8	16.4	18.0
92.5°	22.5	21.7	20.9	20.1	19.3	18.9	19.2	19.8	20.4	21.0	21.6
95°	58.4	51.8	45.2	38.7	32.1	28.8	29.5	30.9	32.3	33.7	35.1
97.5°	105.2	88.8	72.4	56.1	39.7	31.5	33.1	36.3	39.5	42.7	45.9
100°	159.1	131.7	104.4	77.0	49.7	36.0	37.7	41.1	44.4	47.8	51.2
102.5°	218.5	218.1	217.7	217.3	216.9	216.7	198.5	162.1	125.8	89.4	53.0
105°	273.3	279.3	285.3	291.3	297.3	300.3	273.0	218.5	163.9	109.4	54.8
107.5°	337.2	342.2	347.2	352.1	357.1	359.6	325.9	258.6	191.3	123.9	56.6
110°	398.3	402.5	406.7	410.9	415.1	417.2	388.3	330.6	272.8	215.1	157.3

TEST NUMBER: P1009938

CATALOG NUMBER: S122RDIP-B290D925UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	455.9	459.5	463.1	466.6	470.2	472.0	470.3	466.9	463.6	460.2	456.8
115°	517.0	520.4	523.8	527.2	530.6	532.3	534.8	539.8	544.8	549.8	554.8
117.5°	570.0	574.0	578.0	582.0	586.0	588.0	589.7	593.1	596.5	599.9	603.3
120°	629.4	632.4	635.4	638.4	641.4	642.9	644.7	648.3	651.9	655.5	659.1
122.5°	679.7	682.9	686.1	689.3	692.5	694.1	696.1	700.1	704.1	708.1	712.1
125°	731.0	733.6	736.2	738.8	741.4	742.7	744.6	748.4	752.2	756.0	759.8
127.5°	777.7	780.5	783.3	786.1	788.9	790.3	791.8	794.8	797.8	800.8	803.8
130°	821.8	825.0	828.2	831.4	834.6	836.2	837.3	839.5	841.7	843.9	846.1
132.5°	866.8	869.4	872.0	874.5	877.1	878.4	879.5	881.7	883.9	886.1	888.3
135°	904.5	907.7	910.9	914.1	917.3	918.9	919.8	921.6	923.4	925.2	927.0
137.5°	944.1	946.5	948.9	951.3	953.7	954.9	955.9	957.9	959.9	961.9	963.9
140°	982.7	984.3	985.9	987.5	989.1	989.9	991.0	993.2	995.4	997.6	999.8
142.5°	1015.1	1016.5	1017.9	1019.3	1020.7	1021.4	1022.7	1025.3	1027.9	1030.5	1033.1
145°	1049.3	1049.1	1048.9	1048.7	1048.5	1048.4	1050.1	1053.5	1056.9	1060.3	1063.7
147.5°	1078.9	1078.3	1077.7	1077.1	1076.5	1076.2	1077.9	1081.3	1084.7	1088.1	1091.5
150°	1107.7	1106.3	1104.9	1103.5	1102.1	1101.4	1103.0	1106.2	1109.4	1112.6	1115.8
152.5°	1132.0	1130.4	1128.8	1127.2	1125.6	1124.8	1126.3	1129.3	1132.3	1135.3	1138.3
155°	1155.4	1153.6	1151.8	1150.0	1148.2	1147.3	1148.5	1150.9	1153.3	1155.7	1158.1
157.5°	1174.2	1172.6	1171.0	1169.5	1167.9	1167.1	1168.0	1169.8	1171.5	1173.3	1175.1
160°	1190.4	1189.2	1188.0	1186.8	1185.6	1185.0	1185.6	1186.8	1188.0	1189.2	1190.4
162.5°	1204.8	1203.6	1202.4	1201.2	1200.0	1199.4	1199.9	1200.9	1201.9	1202.9	1203.9
165°	1217.4	1216.2	1215.0	1213.8	1212.6	1212.0	1212.3	1212.9	1213.5	1214.1	1214.7
167.5°	1227.3	1226.1	1224.9	1223.7	1222.5	1221.9	1222.2	1222.8	1223.4	1224.0	1224.6
170°	1235.4	1234.2	1233.0	1231.8	1230.6	1230.0	1230.2	1230.6	1231.0	1231.4	1231.8
172.5°	1240.8	1239.6	1238.4	1237.2	1236.0	1235.4	1235.6	1236.0	1236.4	1236.8	1237.2
175°	1245.3	1243.9	1242.5	1241.1	1239.7	1239.0	1239.2	1239.6	1240.0	1240.4	1240.8
177.5°	1247.1	1245.7	1244.3	1242.9	1241.5	1240.8	1240.9	1241.1	1241.3	1241.5	1241.7
180°	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6

TEST NUMBER: P1009938

CATALOG NUMBER: S122RDIP-B290D925UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	654.9	655.8	657.1	663.2	664.1	665.9	665.0	665.0	665.4	664.6	665.0
5°	683.0	684.3	690.9	698.4	700.2	698.4	700.6	703.7	703.7	703.7	702.8
7.5°	709.4	714.2	721.7	732.7	734.9	737.1	741.0	738.4	739.3	743.2	741.9
10°	734.9	741.9	750.3	759.5	764.3	767.4	769.2	773.1	782.4	771.8	775.8
12.5°	759.1	769.2	778.0	788.1	791.6	795.5	796.9	800.4	800.4	799.9	803.0
15°	774.9	784.1	792.0	798.6	799.5	798.6	797.7	798.2	799.5	794.2	797.3
17.5°	778.4	779.3	781.9	779.3	779.7	770.5	765.2	763.9	751.6	752.0	762.1
20°	761.3	746.3	742.4	727.9	719.1	695.3	694.5	687.9	661.9	669.8	668.1
22.5°	714.2	688.7	654.9	638.2	629.8	604.8	585.4	571.8	562.6	553.4	549.4
25°	652.3	610.9	563.0	530.1	525.2	501.9	466.3	449.6	429.9	423.7	434.3
27.5°	572.3	518.6	464.6	414.0	404.8	383.7	365.7	353.8	331.0	329.6	330.5
30°	463.7	409.6	364.4	331.4	308.5	298.9	287.0	278.2	269.0	272.5	273.4
32.5°	381.1	329.6	287.4	269.9	259.3	253.2	243.1	237.3	233.4	232.1	231.6
35°	302.8	268.6	249.7	232.5	226.4	222.0	214.5	211.9	208.3	208.8	208.8
37.5°	259.3	230.8	216.7	207.9	202.2	200.0	195.1	192.5	190.3	189.4	190.8
40°	223.7	203.9	195.1	187.2	182.4	181.5	178.9	175.8	173.2	173.6	174.9
42.5°	197.8	186.4	175.8	169.7	166.1	164.8	162.6	160.4	160.4	159.1	158.7
45°	177.1	167.9	159.1	153.4	151.2	149.4	146.8	146.4	144.6	145.0	145.5
47.5°	158.7	151.2	144.6	138.9	136.7	136.3	133.6	131.9	131.9	131.4	131.0
50°	142.0	134.5	128.8	125.7	122.6	121.7	121.3	120.9	120.0	120.0	120.4
52.5°	128.3	120.9	116.5	113.8	112.1	111.2	111.2	110.8	110.8	110.8	110.3
55°	113.4	107.2	103.7	102.8	102.0	101.5	101.1	100.2	99.8	100.7	99.8
57.5°	99.3	97.1	94.1	93.2	91.0	91.0	89.7	88.8	87.9	88.8	88.8
60°	88.3	85.3	83.5	80.9	79.1	77.4	75.2	74.7	73.8	73.4	73.0
62.5°	76.9	74.3	69.9	65.9	63.3	61.5	60.7	60.2	60.2	59.8	59.8
65°	64.2	58.0	55.8	54.5	54.1	53.6	52.7	52.3	52.7	52.3	52.7
67.5°	50.1	49.2	47.9	47.0	46.6	46.2	46.2	45.7	45.7	45.7	45.7
70°	43.5	41.3	40.9	40.0	40.0	39.6	39.6	39.6	39.6	39.1	40.0
72.5°	36.0	34.7	34.3	33.8	33.8	33.8	33.4	33.4	33.4	33.0	33.4
75°	29.4	29.0	28.1	28.1	27.7	28.1	27.7	27.7	27.3	27.7	27.7
77.5°	23.7	23.3	22.9	22.9	22.4	22.4	22.4	22.4	22.4	22.4	22.9
80°	18.0	17.6	17.1	17.6	17.1	17.6	17.1	17.1	17.6	17.1	17.1
82.5°	13.2	12.7	12.7	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3
85°	7.9	7.5	7.5	7.9	7.5	7.9	7.5	7.5	7.5	7.9	7.9
87.5°	3.5	4.0	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	4.0
90°	19.0	20.0	21.0	22.0	22.5	22.7	23.1	23.5	23.9	24.3	23.9
92.5°	22.0	22.4	22.8	23.2	23.4	23.5	23.7	23.9	24.1	24.3	24.1
95°	36.1	37.1	38.1	39.1	39.6	39.5	39.3	39.1	38.9	38.7	38.9
97.5°	46.5	47.1	47.7	48.3	48.6	48.7	48.9	49.1	49.3	49.5	49.3
100°	52.8	54.4	56.0	57.6	58.4	58.6	59.0	59.4	59.8	60.2	59.8
102.5°	55.2	57.4	59.6	61.8	62.9	63.2	63.8	64.4	65.0	65.6	65.0
105°	57.0	59.2	61.4	63.6	64.7	65.1	65.9	66.7	67.5	68.3	67.5
107.5°	58.8	61.0	63.2	65.4	66.5	66.9	67.7	68.5	69.3	70.1	69.3
110°	137.3	117.3	97.4	77.4	67.4	67.8	68.6	69.4	70.2	71.0	70.2

TEST NUMBER: P1009938

CATALOG NUMBER: S122RDIP-B290D925UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	370.7	284.5	198.4	112.3	69.2	69.5	70.1	70.7	71.3	71.9	71.3
115°	462.3	369.8	277.3	184.8	138.5	131.3	116.9	102.5	88.1	73.7	88.1
117.5°	574.7	546.1	517.6	489.0	474.7	448.5	396.2	343.9	291.5	239.2	291.5
120°	661.5	663.9	666.2	668.6	669.8	656.3	629.4	602.4	575.5	548.5	575.5
122.5°	713.3	714.5	715.7	716.9	717.5	717.6	717.8	718.0	718.2	718.4	718.2
125°	761.2	762.6	763.9	765.3	766.0	766.3	766.9	767.5	768.1	768.7	768.1
127.5°	805.8	807.8	809.8	811.8	812.8	812.9	813.1	813.3	813.5	813.7	813.5
130°	848.3	850.5	852.7	854.9	856.0	855.9	855.7	855.5	855.3	855.1	855.3
132.5°	890.1	891.9	893.7	895.5	896.4	896.3	896.1	895.9	895.7	895.5	895.7
135°	929.0	931.0	933.0	935.0	936.0	935.8	935.4	935.0	934.6	934.2	934.6
137.5°	965.9	967.9	969.8	971.8	972.8	972.5	971.9	971.3	970.7	970.1	970.7
140°	1001.6	1003.4	1005.2	1007.0	1007.9	1007.4	1006.4	1005.4	1004.4	1003.4	1004.4
142.5°	1034.7	1036.3	1037.9	1039.5	1040.3	1039.8	1038.8	1037.8	1036.8	1035.8	1036.8
145°	1065.1	1066.5	1067.9	1069.3	1070.0	1069.5	1068.5	1067.5	1066.5	1065.5	1066.5
147.5°	1092.5	1093.5	1094.5	1095.5	1096.0	1095.6	1094.8	1094.0	1093.2	1092.4	1093.2
150°	1117.0	1118.2	1119.4	1120.6	1121.2	1120.7	1119.7	1118.7	1117.7	1116.7	1117.7
152.5°	1139.5	1140.7	1141.9	1143.1	1143.7	1143.0	1141.6	1140.2	1138.8	1137.4	1138.8
155°	1159.3	1160.5	1161.7	1162.9	1163.5	1162.7	1161.1	1159.5	1157.9	1156.3	1157.9
157.5°	1176.5	1177.9	1179.3	1180.7	1181.4	1180.6	1179.0	1177.4	1175.8	1174.2	1175.8
160°	1191.6	1192.8	1194.0	1195.2	1195.8	1195.1	1193.7	1192.3	1190.9	1189.5	1190.9
162.5°	1205.3	1206.7	1208.1	1209.5	1210.2	1209.3	1207.5	1205.7	1203.9	1202.1	1203.9
165°	1216.1	1217.5	1218.9	1220.3	1221.0	1220.3	1218.9	1217.5	1216.1	1214.7	1216.1
167.5°	1226.0	1227.4	1228.8	1230.2	1230.9	1230.0	1228.2	1226.4	1224.6	1222.8	1224.6
170°	1233.2	1234.6	1236.0	1237.4	1238.1	1237.2	1235.4	1233.6	1231.8	1230.0	1231.8
172.5°	1238.6	1240.0	1241.4	1242.8	1243.5	1242.6	1240.8	1239.0	1237.2	1235.4	1237.2
175°	1242.2	1243.6	1245.0	1246.4	1247.1	1246.1	1244.1	1242.1	1240.1	1238.1	1240.1
177.5°	1243.1	1244.5	1245.9	1247.3	1248.0	1247.1	1245.3	1243.5	1241.7	1239.9	1241.7
180°	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6

TEST NUMBER: P1009938

CATALOG NUMBER: S122RDIP-B290D925UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	666.8	663.7	662.8	663.7	662.8	663.2	660.2	648.7	651.8	647.0	649.6
5°	704.6	701.9	696.2	695.3	694.5	693.6	689.2	679.1	675.1	668.5	668.1
7.5°	740.6	740.6	736.2	733.1	729.2	726.1	720.4	705.4	699.3	691.4	687.0
10°	776.2	764.8	769.6	766.5	756.9	755.1	744.6	735.8	723.9	716.0	709.0
12.5°	801.7	798.2	793.8	791.1	788.5	782.8	775.8	753.3	747.2	731.4	723.5
15°	800.8	798.6	799.9	799.9	799.1	797.7	792.0	775.8	765.2	749.8	736.2
17.5°	757.7	763.5	769.2	773.1	781.9	785.9	791.1	781.5	774.9	761.7	747.2
20°	682.6	696.6	713.4	716.9	724.8	748.1	758.6	767.0	769.6	765.2	753.3
22.5°	578.0	589.8	630.3	629.4	640.8	668.5	699.3	724.3	744.1	755.1	750.7
25°	452.7	469.4	491.0	507.2	544.6	585.9	624.1	664.1	698.4	728.7	736.2
27.5°	342.4	364.4	381.5	403.0	421.9	470.7	520.0	582.4	622.4	679.9	709.8
30°	276.9	287.0	304.2	314.3	323.5	360.9	416.7	478.2	548.5	614.9	666.3
32.5°	236.5	243.5	256.2	260.6	270.3	295.4	330.5	386.8	459.3	539.7	607.4
35°	212.3	219.8	222.4	226.4	234.3	250.1	274.3	315.1	380.6	459.3	540.2
37.5°	191.6	195.6	203.1	205.7	208.3	220.2	236.5	265.0	308.5	373.2	462.8
40°	177.1	179.3	183.3	185.5	187.2	195.6	210.1	229.4	261.5	310.7	393.4
42.5°	161.7	164.4	167.0	169.7	171.9	178.4	187.2	205.7	227.2	264.6	324.4
45°	146.8	148.6	151.6	153.4	156.5	161.7	169.7	182.4	201.7	225.5	273.8
47.5°	133.2	135.4	136.7	138.9	141.1	146.8	154.3	162.6	178.4	201.7	236.9
50°	120.9	123.5	125.3	125.7	127.5	132.7	138.9	148.1	158.2	176.2	207.0
52.5°	112.1	112.5	113.8	115.6	115.2	118.2	123.9	131.0	141.5	156.0	178.4
55°	102.0	103.3	104.2	104.6	104.6	107.2	110.3	116.9	125.3	137.1	156.0
57.5°	89.2	90.5	93.2	94.1	95.4	96.7	98.0	102.4	109.4	120.9	136.3
60°	76.0	76.9	79.6	81.3	82.2	85.7	87.5	91.0	94.9	103.3	117.8
62.5°	61.1	62.0	63.3	65.0	66.8	72.1	76.5	80.0	83.1	88.8	100.7
65°	53.2	53.6	54.5	54.9	55.4	57.6	61.5	66.4	72.1	76.5	83.5
67.5°	46.2	46.6	47.0	47.9	48.3	48.8	50.5	51.9	57.6	63.7	69.0
70°	39.6	40.4	40.9	40.9	41.3	42.2	43.1	44.8	46.6	49.7	56.3
72.5°	33.4	33.8	34.7	34.7	34.7	35.6	36.5	37.4	38.2	40.0	42.6
75°	27.7	28.6	28.6	28.6	29.0	29.0	29.9	30.8	31.6	33.0	33.8
77.5°	22.9	22.9	22.9	22.9	23.3	23.3	23.7	24.6	25.1	25.5	26.4
80°	17.1	17.6	17.6	17.6	18.0	18.0	18.0	18.9	19.3	19.3	20.2
82.5°	12.7	12.7	12.7	13.2	12.7	13.2	13.2	13.6	13.2	13.6	14.1
85°	7.9	7.9	7.9	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.8
87.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.4	4.0	4.0
90°	23.5	23.1	22.7	22.5	22.0	21.0	20.0	19.0	18.0	16.4	14.8
92.5°	23.9	23.7	23.5	23.4	23.2	22.8	22.4	22.0	21.6	21.0	20.4
95°	39.1	39.3	39.5	39.6	39.1	38.1	37.1	36.1	35.1	33.7	32.3
97.5°	49.1	48.9	48.7	48.6	48.3	47.7	47.1	46.5	45.9	42.7	39.5
100°	59.4	59.0	58.6	58.4	57.6	56.0	54.4	52.8	51.2	47.8	44.4
102.5°	64.4	63.8	63.2	62.9	61.8	59.6	57.4	55.2	53.0	49.4	45.8
105°	66.7	65.9	65.1	64.7	63.6	61.4	59.2	57.0	54.8	50.4	46.9
107.5°	68.5	67.7	66.9	66.5	65.4	63.2	61.0	58.8	56.6	52.9	49.3
110°	69.4	68.6	67.8	67.4	77.4	97.4	117.3	137.3	157.3	215.1	272.8

TEST NUMBER: P1009938

CATALOG NUMBER: S122RDIP-B290D925UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	70.7	70.1	69.5	69.2	112.3	198.4	284.5	370.7	456.8	460.2	463.6
115°	102.5	116.9	131.3	138.5	184.8	277.3	369.8	462.3	554.8	549.8	544.8
117.5°	343.9	396.2	448.5	474.7	489.0	517.6	546.1	574.7	603.3	599.9	596.5
120°	602.4	629.4	656.3	669.8	668.6	666.2	663.9	661.5	659.1	655.5	651.9
122.5°	718.0	717.8	717.6	717.5	716.9	715.7	714.5	713.3	712.1	708.1	704.1
125°	767.5	766.9	766.3	766.0	765.3	763.9	762.6	761.2	759.8	756.0	752.2
127.5°	813.3	813.1	812.9	812.8	811.8	809.8	807.8	805.8	803.8	800.8	797.8
130°	855.5	855.7	855.9	856.0	854.9	852.7	850.5	848.3	846.1	843.9	841.7
132.5°	895.9	896.1	896.3	896.4	895.5	893.7	891.9	890.1	888.3	886.1	883.9
135°	935.0	935.4	935.8	936.0	935.0	933.0	931.0	929.0	927.0	925.2	923.4
137.5°	971.3	971.9	972.5	972.8	971.8	969.8	967.9	965.9	963.9	961.9	959.9
140°	1005.4	1006.4	1007.4	1007.9	1007.0	1005.2	1003.4	1001.6	999.8	997.6	995.4
142.5°	1037.8	1038.8	1039.8	1040.3	1039.5	1037.9	1036.3	1034.7	1033.1	1030.5	1027.9
145°	1067.5	1068.5	1069.5	1070.0	1069.3	1067.9	1066.5	1065.1	1063.7	1060.3	1056.9
147.5°	1094.0	1094.8	1095.6	1096.0	1095.5	1094.5	1093.5	1092.5	1091.5	1088.1	1084.7
150°	1118.7	1119.7	1120.7	1121.2	1120.6	1119.4	1118.2	1117.0	1115.8	1112.6	1109.4
152.5°	1140.2	1141.6	1143.0	1143.7	1143.1	1141.9	1140.7	1139.5	1138.3	1135.3	1132.3
155°	1159.5	1161.1	1162.7	1163.5	1162.9	1161.7	1160.5	1159.3	1158.1	1155.7	1153.3
157.5°	1177.4	1179.0	1180.6	1181.4	1180.7	1179.3	1177.9	1176.5	1175.1	1173.3	1171.5
160°	1192.3	1193.7	1195.1	1195.8	1195.2	1194.0	1192.8	1191.6	1190.4	1189.2	1188.0
162.5°	1205.7	1207.5	1209.3	1210.2	1209.5	1208.1	1206.7	1205.3	1203.9	1202.9	1201.9
165°	1217.5	1218.9	1220.3	1221.0	1220.3	1218.9	1217.5	1216.1	1214.7	1214.1	1213.5
167.5°	1226.4	1228.2	1230.0	1230.9	1230.2	1228.8	1227.4	1226.0	1224.6	1224.0	1223.4
170°	1233.6	1235.4	1237.2	1238.1	1237.4	1236.0	1234.6	1233.2	1231.8	1231.4	1231.0
172.5°	1239.0	1240.8	1242.6	1243.5	1242.8	1241.4	1240.0	1238.6	1237.2	1236.8	1236.4
175°	1242.1	1244.1	1246.1	1247.1	1246.4	1245.0	1243.6	1242.2	1240.8	1240.4	1240.0
177.5°	1243.5	1245.3	1247.1	1248.0	1247.3	1245.9	1244.5	1243.1	1241.7	1241.5	1241.3
180°	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6

TEST NUMBER: P1009938

CATALOG NUMBER: S122RDIP-B290D925UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	645.7	643.5	643.5	642.1	642.1	635.1	635.1	637.3	634.7	631.6	627.2
5°	662.4	657.5	656.2	654.5	648.7	639.9	636.4	635.1	629.8	623.2	615.8
7.5°	678.2	670.3	666.3	662.4	654.9	642.6	635.6	630.7	622.8	612.7	603.0
10°	693.6	683.5	673.4	668.5	658.0	642.6	632.5	624.6	613.1	599.5	585.9
12.5°	707.6	686.5	684.8	675.1	659.7	642.1	626.8	615.3	600.8	585.0	569.2
15°	719.9	698.4	687.9	679.1	658.8	636.9	620.6	606.5	587.2	569.2	549.8
17.5°	726.1	702.8	695.8	681.3	660.6	632.0	610.1	592.9	571.8	550.3	528.3
20°	732.3	705.0	693.6	683.5	655.3	622.8	598.2	578.4	555.1	529.6	505.5
22.5°	735.3	705.0	691.4	677.3	650.1	612.7	583.7	560.4	533.1	507.2	478.2
25°	730.1	702.4	686.1	671.6	640.8	600.4	567.0	540.6	511.6	482.2	452.7
27.5°	716.9	696.2	677.3	662.4	628.1	584.6	549.4	519.5	489.6	456.7	426.8
30°	692.3	683.0	668.1	651.4	614.0	570.5	528.7	498.0	465.0	432.1	400.8
32.5°	654.0	661.9	652.3	637.8	597.3	551.2	506.8	475.6	439.5	403.9	375.4
35°	607.4	635.6	630.3	620.2	579.7	530.5	486.1	448.3	412.3	376.2	347.7
37.5°	556.4	599.1	603.5	597.3	559.5	509.4	460.6	423.7	386.8	350.3	321.3
40°	486.6	552.0	566.1	568.7	538.4	483.9	432.9	396.9	360.4	324.8	289.6
42.5°	422.4	505.0	522.6	533.6	511.6	458.9	407.4	367.4	331.4	299.3	264.2
45°	362.2	448.3	476.9	491.0	481.3	430.3	377.1	339.8	306.8	277.3	243.5
47.5°	300.2	386.8	426.8	449.2	449.2	401.3	348.1	311.2	279.5	254.5	224.6
50°	258.9	331.0	372.3	401.7	409.6	371.8	321.7	285.7	255.8	228.6	205.7
52.5°	220.6	285.3	319.5	350.3	373.2	340.2	292.3	259.8	230.3	204.8	186.8
55°	190.8	239.1	270.3	304.2	329.6	308.1	263.7	232.1	206.6	185.5	170.1
57.5°	162.2	204.4	229.9	259.8	287.0	270.7	235.1	207.9	185.5	167.0	153.4
60°	138.0	172.3	192.1	215.4	249.2	237.8	208.3	183.3	165.3	148.6	137.1
62.5°	117.4	144.6	161.3	178.0	208.8	203.5	180.6	161.3	145.9	131.9	122.2
65°	96.3	118.7	131.9	146.4	171.0	173.2	154.7	141.1	127.0	114.7	105.9
67.5°	77.8	95.4	107.2	119.6	139.3	145.5	132.7	121.3	109.4	99.3	91.4
70°	62.9	75.2	83.9	93.6	109.9	117.4	110.8	102.8	93.2	84.8	77.8
72.5°	49.7	57.6	62.9	70.3	83.5	91.0	90.5	83.5	76.5	70.8	65.0
75°	36.5	42.6	47.0	51.9	62.4	69.4	71.2	68.1	61.1	56.7	52.3
77.5°	27.7	31.2	33.4	36.9	44.4	50.5	53.2	52.3	47.5	44.0	40.9
80°	21.1	22.0	22.9	24.2	30.3	36.0	37.8	37.4	34.7	33.4	29.9
82.5°	14.9	15.4	15.8	16.3	18.5	23.3	25.1	25.9	23.7	22.4	19.3
85°	8.8	9.2	9.2	10.1	10.5	11.9	14.9	14.9	14.5	12.7	12.3
87.5°	4.4	4.4	4.0	4.0	4.4	4.8	5.7	6.6	5.7	5.3	4.8
90°	13.2	11.6	10.8	9.7	7.5	5.3	3.1	0.9	3.1	5.3	7.5
92.5°	19.8	19.2	18.9	19.3	20.1	20.9	21.7	22.5	21.7	20.9	20.1
95°	30.9	29.5	28.8	32.1	38.7	45.2	51.8	58.4	51.8	45.2	38.7
97.5°	36.3	33.1	31.5	39.7	56.1	72.4	88.8	105.2	88.8	72.4	56.1
100°	41.1	37.7	36.0	49.7	77.0	104.4	131.7	159.1	131.7	104.4	77.0
102.5°	162.1	198.5	216.7	216.9	217.3	217.7	218.1	218.5	218.1	217.7	217.3
105°	218.5	273.0	300.3	297.3	291.3	285.3	279.3	273.3	279.3	285.3	291.3
107.5°	258.6	325.9	359.6	357.1	352.1	347.2	342.2	337.2	342.2	347.2	352.1
110°	330.6	388.3	417.2	415.1	410.9	406.7	402.5	398.3	402.5	406.7	410.9

TEST NUMBER: P1009938

CATALOG NUMBER: S122RDIP-B290D925UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	466.9	470.3	472.0	470.2	466.6	463.1	459.5	455.9	459.5	463.1	466.6
115°	539.8	534.8	532.3	530.6	527.2	523.8	520.4	517.0	520.4	523.8	527.2
117.5°	593.1	589.7	588.0	586.0	582.0	578.0	574.0	570.0	574.0	578.0	582.0
120°	648.3	644.7	642.9	641.4	638.4	635.4	632.4	629.4	632.4	635.4	638.4
122.5°	700.1	696.1	694.1	692.5	689.3	686.1	682.9	679.7	682.9	686.1	689.3
125°	748.4	744.6	742.7	741.4	738.8	736.2	733.6	731.0	733.6	736.2	738.8
127.5°	794.8	791.8	790.3	788.9	786.1	783.3	780.5	777.7	780.5	783.3	786.1
130°	839.5	837.3	836.2	834.6	831.4	828.2	825.0	821.8	825.0	828.2	831.4
132.5°	881.7	879.5	878.4	877.1	874.5	872.0	869.4	866.8	869.4	872.0	874.5
135°	921.6	919.8	918.9	917.3	914.1	910.9	907.7	904.5	907.7	910.9	914.1
137.5°	957.9	955.9	954.9	953.7	951.3	948.9	946.5	944.1	946.5	948.9	951.3
140°	993.2	991.0	989.9	989.1	987.5	985.9	984.3	982.7	984.3	985.9	987.5
142.5°	1025.3	1022.7	1021.4	1020.7	1019.3	1017.9	1016.5	1015.1	1016.5	1017.9	1019.3
145°	1053.5	1050.1	1048.4	1048.5	1048.7	1048.9	1049.1	1049.3	1049.1	1048.9	1048.7
147.5°	1081.3	1077.9	1076.2	1076.5	1077.1	1077.7	1078.3	1078.9	1078.3	1077.7	1077.1
150°	1106.2	1103.0	1101.4	1102.1	1103.5	1104.9	1106.3	1107.7	1106.3	1104.9	1103.5
152.5°	1129.3	1126.3	1124.8	1125.6	1127.2	1128.8	1130.4	1132.0	1130.4	1128.8	1127.2
155°	1150.9	1148.5	1147.3	1148.2	1150.0	1151.8	1153.6	1155.4	1153.6	1151.8	1150.0
157.5°	1169.8	1168.0	1167.1	1167.9	1169.5	1171.0	1172.6	1174.2	1172.6	1171.0	1169.5
160°	1186.8	1185.6	1185.0	1185.6	1186.8	1188.0	1189.2	1190.4	1189.2	1188.0	1186.8
162.5°	1200.9	1199.9	1199.4	1200.0	1201.2	1202.4	1203.6	1204.8	1203.6	1202.4	1201.2
165°	1212.9	1212.3	1212.0	1212.6	1213.8	1215.0	1216.2	1217.4	1216.2	1215.0	1213.8
167.5°	1222.8	1222.2	1221.9	1222.5	1223.7	1224.9	1226.1	1227.3	1226.1	1224.9	1223.7
170°	1230.6	1230.2	1230.0	1230.6	1231.8	1233.0	1234.2	1235.4	1234.2	1233.0	1231.8
172.5°	1236.0	1235.6	1235.4	1236.0	1237.2	1238.4	1239.6	1240.8	1239.6	1238.4	1237.2
175°	1239.6	1239.2	1239.0	1239.7	1241.1	1242.5	1243.9	1245.3	1243.9	1242.5	1241.1
177.5°	1241.1	1240.9	1240.8	1241.5	1242.9	1244.3	1245.7	1247.1	1245.7	1244.3	1242.9
180°	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6

TEST NUMBER: P1009938

CATALOG NUMBER: S122RDIP-B290D925UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	625.4	625.9	627.2	623.2	617.1	614.5	606.5	605.2	603.9	603.9	605.2
5°	611.4	609.6	610.1	602.6	593.8	588.5	577.5	579.3	573.6	570.1	570.9
7.5°	596.0	591.2	590.7	581.1	570.1	560.4	549.0	546.3	541.1	534.9	532.3
10°	576.7	573.1	566.5	555.6	541.5	533.6	518.2	509.0	507.7	498.4	494.9
12.5°	556.9	550.7	544.1	528.7	512.9	500.2	488.8	478.6	471.6	463.7	458.4
15°	534.0	526.6	519.1	502.8	484.4	471.6	454.5	439.5	418.9	402.6	393.4
17.5°	509.0	500.6	490.5	472.5	454.5	436.9	405.2	387.7	373.2	363.5	357.8
20°	483.0	473.8	463.7	445.7	414.5	383.7	366.1	352.5	343.7	334.0	327.0
22.5°	455.8	446.1	435.1	407.0	374.0	352.5	338.9	326.1	313.4	308.1	304.6
25°	430.3	421.5	407.4	369.2	343.3	323.5	308.1	299.8	293.2	286.1	279.5
27.5°	403.9	387.7	367.9	335.8	319.5	299.3	288.3	282.2	270.7	265.9	262.8
30°	372.3	354.3	335.4	312.5	293.6	279.5	269.4	259.3	252.7	247.9	242.6
32.5°	340.2	323.1	311.2	287.4	273.4	258.9	249.2	243.1	233.4	230.3	228.1
35°	312.5	298.0	287.4	268.1	254.9	241.7	234.7	225.5	219.3	213.6	210.1
37.5°	285.3	277.3	266.4	250.1	236.0	225.5	215.8	212.7	204.4	201.3	197.8
40°	266.4	254.5	245.3	231.2	219.3	207.9	201.7	194.7	189.0	184.2	182.8
42.5°	243.5	234.7	229.4	214.0	201.7	195.1	187.7	179.8	175.4	171.4	166.6
45°	226.4	218.4	211.0	198.7	187.7	179.3	172.7	167.5	160.0	158.2	150.8
47.5°	208.3	200.4	194.7	182.4	172.3	164.4	159.5	152.5	146.4	142.4	138.9
50°	190.3	183.7	178.4	167.9	159.1	150.8	144.2	137.1	134.5	127.9	125.7
52.5°	173.2	168.8	163.1	153.0	144.2	137.1	130.1	124.4	120.4	116.9	114.3
55°	158.7	151.6	149.0	138.0	130.5	123.1	116.9	113.4	108.6	106.4	104.2
57.5°	142.4	138.5	134.1	125.7	117.4	110.3	105.9	100.7	98.0	95.4	93.6
60°	128.3	122.6	119.1	112.1	104.6	98.0	94.1	90.1	86.6	84.4	80.9
62.5°	112.1	107.7	105.5	98.0	91.9	85.7	82.2	78.2	75.6	71.6	67.2
65°	98.0	94.5	91.9	85.7	80.0	74.3	70.8	65.9	62.4	60.2	59.8
67.5°	85.7	83.1	79.1	73.4	67.7	63.3	59.3	55.4	54.9	54.1	54.1
70°	72.1	69.4	67.2	61.1	56.3	51.4	50.5	49.2	47.9	47.5	46.6
72.5°	60.2	58.0	55.4	50.1	45.3	44.0	43.1	42.2	40.9	40.4	40.0
75°	48.8	45.7	44.0	39.1	37.8	36.9	36.0	34.7	33.8	33.4	32.5
77.5°	37.4	34.3	34.3	31.6	30.8	29.4	28.6	27.7	27.3	26.4	26.4
80°	26.4	26.4	25.5	24.2	22.9	22.4	21.1	20.7	20.2	20.7	19.8
82.5°	19.3	17.6	17.6	16.7	15.8	15.4	14.5	14.5	14.1	14.1	14.1
85°	11.0	11.0	10.5	9.7	9.2	9.2	8.8	8.8	8.4	8.4	7.9
87.5°	4.4	4.0	4.4	4.0	4.0	3.5	3.5	3.5	3.1	3.5	3.1
90°	9.7	10.8	11.6	13.2	14.8	16.4	18.0	19.0	20.0	21.0	22.0
92.5°	19.3	18.9	19.2	19.8	20.4	21.0	21.6	22.0	22.4	22.8	23.2
95°	32.1	28.8	29.5	30.9	32.3	33.7	35.1	36.1	37.1	38.1	39.1
97.5°	39.7	31.5	33.1	36.3	39.5	42.7	45.9	46.5	47.1	47.7	48.3
100°	49.7	36.0	37.7	41.1	44.4	47.8	51.2	52.8	54.4	56.0	57.6
102.5°	216.9	216.7	198.5	162.1	125.8	89.4	53.0	55.2	57.4	59.6	61.8
105°	297.3	300.3	273.0	218.5	163.9	109.4	54.8	57.0	59.2	61.4	63.6
107.5°	357.1	359.6	325.9	258.6	191.3	123.9	56.6	58.8	61.0	63.2	65.4
110°	415.1	417.2	388.3	330.6	272.8	215.1	157.3	137.3	117.3	97.4	77.4

TEST NUMBER: P1009938

CATALOG NUMBER: S122RDIP-B290D925UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	470.2	472.0	470.3	466.9	463.6	460.2	456.8	370.7	284.5	198.4	112.3
115°	530.6	532.3	534.8	539.8	544.8	549.8	554.8	462.3	369.8	277.3	184.8
117.5°	586.0	588.0	589.7	593.1	596.5	599.9	603.3	574.7	546.1	517.6	489.0
120°	641.4	642.9	644.7	648.3	651.9	655.5	659.1	661.5	663.9	666.2	668.6
122.5°	692.5	694.1	696.1	700.1	704.1	708.1	712.1	713.3	714.5	715.7	716.9
125°	741.4	742.7	744.6	748.4	752.2	756.0	759.8	761.2	762.6	763.9	765.3
127.5°	788.9	790.3	791.8	794.8	797.8	800.8	803.8	805.8	807.8	809.8	811.8
130°	834.6	836.2	837.3	839.5	841.7	843.9	846.1	848.3	850.5	852.7	854.9
132.5°	877.1	878.4	879.5	881.7	883.9	886.1	888.3	890.1	891.9	893.7	895.5
135°	917.3	918.9	919.8	921.6	923.4	925.2	927.0	929.0	931.0	933.0	935.0
137.5°	953.7	954.9	955.9	957.9	959.9	961.9	963.9	965.9	967.9	969.8	971.8
140°	989.1	989.9	991.0	993.2	995.4	997.6	999.8	1001.6	1003.4	1005.2	1007.0
142.5°	1020.7	1021.4	1022.7	1025.3	1027.9	1030.5	1033.1	1034.7	1036.3	1037.9	1039.5
145°	1048.5	1048.4	1050.1	1053.5	1056.9	1060.3	1063.7	1065.1	1066.5	1067.9	1069.3
147.5°	1076.5	1076.2	1077.9	1081.3	1084.7	1088.1	1091.5	1092.5	1093.5	1094.5	1095.5
150°	1102.1	1101.4	1103.0	1106.2	1109.4	1112.6	1115.8	1117.0	1118.2	1119.4	1120.6
152.5°	1125.6	1124.8	1126.3	1129.3	1132.3	1135.3	1138.3	1139.5	1140.7	1141.9	1143.1
155°	1148.2	1147.3	1148.5	1150.9	1153.3	1155.7	1158.1	1159.3	1160.5	1161.7	1162.9
157.5°	1167.9	1167.1	1168.0	1169.8	1171.5	1173.3	1175.1	1176.5	1177.9	1179.3	1180.7
160°	1185.6	1185.0	1185.6	1186.8	1188.0	1189.2	1190.4	1191.6	1192.8	1194.0	1195.2
162.5°	1200.0	1199.4	1199.9	1200.9	1201.9	1202.9	1203.9	1205.3	1206.7	1208.1	1209.5
165°	1212.6	1212.0	1212.3	1212.9	1213.5	1214.1	1214.7	1216.1	1217.5	1218.9	1220.3
167.5°	1222.5	1221.9	1222.2	1222.8	1223.4	1224.0	1224.6	1226.0	1227.4	1228.8	1230.2
170°	1230.6	1230.0	1230.2	1230.6	1231.0	1231.4	1231.8	1233.2	1234.6	1236.0	1237.4
172.5°	1236.0	1235.4	1235.6	1236.0	1236.4	1236.8	1237.2	1238.6	1240.0	1241.4	1242.8
175°	1239.7	1239.0	1239.2	1239.6	1240.0	1240.4	1240.8	1242.2	1243.6	1245.0	1246.4
177.5°	1241.5	1240.8	1240.9	1241.1	1241.3	1241.5	1241.7	1243.1	1244.5	1245.9	1247.3
180°	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6

TEST NUMBER: P1009938

CATALOG NUMBER: S122RDIP-B290D925UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	605.2	604.3	601.7	602.6	601.3	601.3	600.4	600.4	600.4	602.6	601.3
5°	572.3	569.2	566.1	564.8	563.5	562.2	562.2	561.7	565.7	564.8	568.3
7.5°	531.4	530.5	524.4	524.4	522.2	521.3	523.5	523.9	524.4	525.2	527.4
10°	494.9	492.7	483.9	484.8	483.5	481.7	483.0	482.2	485.2	486.1	485.2
12.5°	451.8	447.9	438.2	433.4	428.1	424.1	429.0	425.5	437.8	441.3	451.0
15°	394.7	387.2	380.6	380.6	375.8	372.3	374.5	378.4	381.1	385.0	386.8
17.5°	356.5	353.4	348.1	345.0	343.7	342.4	342.4	344.1	349.9	349.4	352.9
20°	323.9	322.2	319.5	315.6	314.3	313.4	313.4	313.4	317.3	320.9	323.1
22.5°	301.5	300.2	298.4	293.2	290.5	289.6	291.8	293.2	296.2	298.9	301.1
25°	279.1	276.0	272.9	271.2	269.9	269.9	270.7	271.2	272.5	273.8	276.5
27.5°	260.6	258.4	254.0	249.2	249.2	247.9	248.8	249.7	252.7	257.1	259.3
30°	240.0	239.5	237.8	236.0	234.3	233.4	235.1	236.5	236.9	239.1	239.1
32.5°	225.0	222.0	218.9	217.1	216.2	215.8	216.2	218.0	218.0	220.6	223.7
35°	210.1	208.3	205.3	202.2	201.3	199.1	200.9	202.6	205.7	207.0	208.3
37.5°	193.8	191.6	190.3	189.4	187.7	188.1	186.8	189.4	192.1	191.6	192.5
40°	181.5	177.6	173.6	173.2	172.7	172.3	172.3	172.7	174.5	176.2	178.9
42.5°	165.7	164.4	160.9	157.4	156.5	155.6	154.7	156.5	160.0	163.1	164.4
45°	149.4	147.7	146.8	144.2	142.4	142.0	141.1	143.3	146.4	147.7	148.6
47.5°	134.5	134.1	131.4	131.9	130.5	131.0	130.5	131.9	131.9	133.2	134.1
50°	124.4	123.1	121.7	120.9	119.6	119.6	119.1	119.6	121.3	123.1	122.6
52.5°	114.3	112.1	111.6	111.2	110.3	111.2	109.9	110.3	112.1	113.0	112.5
55°	102.4	102.0	101.1	100.2	99.8	99.3	99.3	99.3	101.1	102.4	102.8
57.5°	93.2	91.0	89.2	89.2	87.5	87.0	87.9	88.3	89.7	90.5	91.4
60°	80.4	79.6	76.9	75.6	73.0	72.5	72.5	74.3	76.5	79.6	80.4
62.5°	66.8	65.5	65.0	65.0	65.0	65.0	65.0	65.0	65.0	65.5	65.5
65°	59.3	59.8	59.3	58.9	59.3	59.3	58.9	58.9	58.9	59.3	59.8
67.5°	53.2	52.7	53.2	52.7	52.3	52.3	51.9	52.3	52.7	53.2	53.2
70°	46.2	46.2	45.7	46.2	45.7	45.3	44.8	44.8	45.7	46.2	46.2
72.5°	39.6	39.6	39.1	39.1	38.2	38.2	38.7	38.2	38.2	39.6	39.6
75°	33.0	32.5	32.1	32.1	31.6	31.6	31.6	31.2	32.1	32.1	32.5
77.5°	25.9	25.9	25.9	25.5	25.5	25.1	25.1	25.5	25.5	25.5	25.9
80°	19.8	19.8	19.8	19.3	18.9	18.9	18.9	18.9	18.9	19.3	18.9
82.5°	13.6	13.6	13.6	13.6	13.6	13.2	13.2	13.2	13.6	13.6	13.2
85°	8.4	7.9	8.4	8.4	7.9	8.4	7.9	7.9	7.5	7.5	7.9
87.5°	3.5	3.1	2.6	2.6	3.1	2.6	2.6	2.6	3.1	2.6	2.6
90°	22.5	22.7	23.1	23.5	23.9	24.3	23.9	23.5	23.1	22.7	22.5
92.5°	23.4	23.5	23.7	23.9	24.1	24.3	24.1	23.9	23.7	23.5	23.4
95°	39.6	39.5	39.3	39.1	38.9	38.7	38.9	39.1	39.3	39.5	39.6
97.5°	48.6	48.7	48.9	49.1	49.3	49.5	49.3	49.1	48.9	48.7	48.6
100°	58.4	58.6	59.0	59.4	59.8	60.2	59.8	59.4	59.0	58.6	58.4
102.5°	62.9	63.2	63.8	64.4	65.0	65.6	65.0	64.4	63.8	63.2	62.9
105°	64.7	65.1	65.9	66.7	67.5	68.3	67.5	66.7	65.9	65.1	64.7
107.5°	66.5	66.9	67.7	68.5	69.3	70.1	69.3	68.5	67.7	66.9	66.5
110°	67.4	67.8	68.6	69.4	70.2	71.0	70.2	69.4	68.6	67.8	67.4

TEST NUMBER: P1009938

CATALOG NUMBER: S122RDIP-B290D925UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	69.2	69.5	70.1	70.7	71.3	71.9	71.3	70.7	70.1	69.5	69.2
115°	138.5	131.3	116.9	102.5	88.1	73.7	88.1	102.5	116.9	131.3	138.5
117.5°	474.7	448.5	396.2	343.9	291.5	239.2	291.5	343.9	396.2	448.5	474.7
120°	669.8	656.3	629.4	602.4	575.5	548.5	575.5	602.4	629.4	656.3	669.8
122.5°	717.5	717.6	717.8	718.0	718.2	718.4	718.2	718.0	717.8	717.6	717.5
125°	766.0	766.3	766.9	767.5	768.1	768.7	768.1	767.5	766.9	766.3	766.0
127.5°	812.8	812.9	813.1	813.3	813.5	813.7	813.5	813.3	813.1	812.9	812.8
130°	856.0	855.9	855.7	855.5	855.3	855.1	855.3	855.5	855.7	855.9	856.0
132.5°	896.4	896.3	896.1	895.9	895.7	895.5	895.7	895.9	896.1	896.3	896.4
135°	936.0	935.8	935.4	935.0	934.6	934.2	934.6	935.0	935.4	935.8	936.0
137.5°	972.8	972.5	971.9	971.3	970.7	970.1	970.7	971.3	971.9	972.5	972.8
140°	1007.9	1007.4	1006.4	1005.4	1004.4	1003.4	1004.4	1005.4	1006.4	1007.4	1007.9
142.5°	1040.3	1039.8	1038.8	1037.8	1036.8	1035.8	1036.8	1037.8	1038.8	1039.8	1040.3
145°	1070.0	1069.5	1068.5	1067.5	1066.5	1065.5	1066.5	1067.5	1068.5	1069.5	1070.0
147.5°	1096.0	1095.6	1094.8	1094.0	1093.2	1092.4	1093.2	1094.0	1094.8	1095.6	1096.0
150°	1121.2	1120.7	1119.7	1118.7	1117.7	1116.7	1117.7	1118.7	1119.7	1120.7	1121.2
152.5°	1143.7	1143.0	1141.6	1140.2	1138.8	1137.4	1138.8	1140.2	1141.6	1143.0	1143.7
155°	1163.5	1162.7	1161.1	1159.5	1157.9	1156.3	1157.9	1159.5	1161.1	1162.7	1163.5
157.5°	1181.4	1180.6	1179.0	1177.4	1175.8	1174.2	1175.8	1177.4	1179.0	1180.6	1181.4
160°	1195.8	1195.1	1193.7	1192.3	1190.9	1189.5	1190.9	1192.3	1193.7	1195.1	1195.8
162.5°	1210.2	1209.3	1207.5	1205.7	1203.9	1202.1	1203.9	1205.7	1207.5	1209.3	1210.2
165°	1221.0	1220.3	1218.9	1217.5	1216.1	1214.7	1216.1	1217.5	1218.9	1220.3	1221.0
167.5°	1230.9	1230.0	1228.2	1226.4	1224.6	1222.8	1224.6	1226.4	1228.2	1230.0	1230.9
170°	1238.1	1237.2	1235.4	1233.6	1231.8	1230.0	1231.8	1233.6	1235.4	1237.2	1238.1
172.5°	1243.5	1242.6	1240.8	1239.0	1237.2	1235.4	1237.2	1239.0	1240.8	1242.6	1243.5
175°	1247.1	1246.1	1244.1	1242.1	1240.1	1238.1	1240.1	1242.1	1244.1	1246.1	1247.1
177.5°	1248.0	1247.1	1245.3	1243.5	1241.7	1239.9	1241.7	1243.5	1245.3	1247.1	1248.0
180°	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6

TEST NUMBER: P1009938

CATALOG NUMBER: S122RDIP-B290D925UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5	632.5
2.5°	602.6	604.8	603.9	599.1	603.9	605.2	607.9	610.5	612.3	614.9	617.1
5°	564.8	569.2	571.8	569.2	578.0	579.3	585.4	589.0	594.2	598.6	602.2
7.5°	529.2	532.7	538.0	538.9	544.1	550.3	559.1	567.9	576.2	580.6	584.6
10°	491.0	497.1	505.0	503.3	511.2	520.8	530.1	544.1	551.2	559.1	566.1
12.5°	452.7	456.7	467.2	470.7	482.2	489.6	502.4	511.2	528.7	538.0	544.1
15°	385.9	402.2	415.4	431.2	446.1	460.2	471.6	487.4	502.8	509.9	520.0
17.5°	355.6	363.0	371.0	378.9	398.2	423.3	443.5	460.6	473.8	483.0	494.9
20°	323.9	331.4	340.2	347.7	359.5	377.6	402.6	432.1	447.9	457.5	469.0
22.5°	301.5	308.5	314.3	320.9	330.1	343.3	362.2	398.6	419.7	431.6	441.7
25°	277.3	286.1	292.3	297.1	304.6	319.1	334.5	355.1	392.9	402.2	416.2
27.5°	260.6	263.3	270.3	277.8	285.3	293.2	309.0	326.6	352.1	372.3	389.4
30°	240.9	247.5	254.0	257.1	263.7	275.1	284.8	303.7	323.5	339.3	360.0
32.5°	225.9	229.9	234.3	241.7	247.9	255.8	265.5	281.3	298.0	308.1	323.9
35°	209.2	211.9	221.1	224.2	230.3	238.2	247.9	260.2	278.2	286.1	297.6
37.5°	193.4	199.5	202.2	209.2	214.9	222.8	229.9	243.9	255.8	265.0	275.6
40°	181.1	183.7	188.6	194.7	199.5	205.7	214.5	224.6	237.3	244.8	254.0
42.5°	166.1	168.3	174.5	178.0	185.9	191.6	196.9	209.2	220.6	226.4	235.6
45°	149.9	155.2	159.1	166.1	170.5	177.6	184.2	193.0	203.5	210.1	215.4
47.5°	135.8	141.1	145.0	151.6	158.7	161.7	168.8	178.0	187.7	193.0	200.4
50°	124.4	126.1	133.6	136.7	144.2	150.3	155.2	163.1	173.6	176.7	182.8
52.5°	113.4	114.7	119.6	123.5	130.1	135.4	141.5	149.0	157.8	162.6	167.5
55°	103.7	104.6	106.8	111.2	115.6	122.2	127.9	134.9	142.4	147.7	152.1
57.5°	92.7	94.5	96.3	98.9	103.3	109.4	115.6	122.2	128.3	131.9	137.6
60°	80.0	82.6	85.7	88.8	91.9	96.3	103.3	109.4	115.2	118.2	122.6
62.5°	66.4	71.6	74.3	77.8	80.4	84.4	89.7	96.7	100.7	104.6	108.1
65°	59.8	60.2	60.7	64.2	69.0	73.0	77.8	83.1	89.2	91.9	94.5
67.5°	53.2	53.6	54.5	54.9	56.7	61.1	66.4	72.1	76.9	78.7	81.3
70°	46.6	46.6	48.3	48.8	49.2	49.7	54.1	59.8	64.2	66.4	69.4
72.5°	39.6	40.0	40.9	41.3	42.2	43.1	44.4	47.5	52.7	54.9	58.5
75°	32.5	33.0	33.4	33.8	35.2	35.6	36.9	38.7	40.9	43.5	45.7
77.5°	25.9	25.9	26.4	27.3	28.1	28.6	29.9	30.8	31.6	33.0	34.7
80°	19.3	19.8	19.8	20.7	20.7	21.1	21.5	22.9	23.7	24.6	25.5
82.5°	13.2	14.1	14.1	14.1	14.5	14.9	15.4	15.4	16.3	16.7	18.0
85°	7.9	8.4	8.4	8.4	7.9	8.8	8.8	9.2	9.2	9.2	9.7
87.5°	3.1	2.6	3.1	3.1	3.1	3.5	3.1	3.1	3.5	4.0	4.0
90°	22.0	21.0	20.0	19.0	18.0	16.4	14.8	13.2	11.6	10.8	9.7
92.5°	23.2	22.8	22.4	22.0	21.6	21.0	20.4	19.8	19.2	18.9	19.3
95°	39.1	38.1	37.1	36.1	35.1	33.7	32.3	30.9	29.5	28.8	32.1
97.5°	48.3	47.7	47.1	46.5	45.9	42.7	39.5	36.3	33.1	31.5	39.7
100°	57.6	56.0	54.4	52.8	51.2	47.8	44.4	41.1	37.7	36.0	49.7
102.5°	61.8	59.6	57.4	55.2	53.0	89.4	125.8	162.1	198.5	216.7	216.9
105°	63.6	61.4	59.2	57.0	54.8	109.4	163.9	218.5	273.0	300.3	297.3
107.5°	65.4	63.2	61.0	58.8	56.6	123.9	191.3	258.6	325.9	359.6	357.1
110°	77.4	97.4	117.3	137.3	157.3	215.1	272.8	330.6	388.3	417.2	415.1

TEST NUMBER: P1009938

CATALOG NUMBER: S122RDIP-B290D925UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	112.3	198.4	284.5	370.7	456.8	460.2	463.6	466.9	470.3	472.0	470.2
115°	184.8	277.3	369.8	462.3	554.8	549.8	544.8	539.8	534.8	532.3	530.6
117.5°	489.0	517.6	546.1	574.7	603.3	599.9	596.5	593.1	589.7	588.0	586.0
120°	668.6	666.2	663.9	661.5	659.1	655.5	651.9	648.3	644.7	642.9	641.4
122.5°	716.9	715.7	714.5	713.3	712.1	708.1	704.1	700.1	696.1	694.1	692.5
125°	765.3	763.9	762.6	761.2	759.8	756.0	752.2	748.4	744.6	742.7	741.4
127.5°	811.8	809.8	807.8	805.8	803.8	800.8	797.8	794.8	791.8	790.3	788.9
130°	854.9	852.7	850.5	848.3	846.1	843.9	841.7	839.5	837.3	836.2	834.6
132.5°	895.5	893.7	891.9	890.1	888.3	886.1	883.9	881.7	879.5	878.4	877.1
135°	935.0	933.0	931.0	929.0	927.0	925.2	923.4	921.6	919.8	918.9	917.3
137.5°	971.8	969.8	967.9	965.9	963.9	961.9	959.9	957.9	955.9	954.9	953.7
140°	1007.0	1005.2	1003.4	1001.6	999.8	997.6	995.4	993.2	991.0	989.9	989.1
142.5°	1039.5	1037.9	1036.3	1034.7	1033.1	1030.5	1027.9	1025.3	1022.7	1021.4	1020.7
145°	1069.3	1067.9	1066.5	1065.1	1063.7	1060.3	1056.9	1053.5	1050.1	1048.4	1048.5
147.5°	1095.5	1094.5	1093.5	1092.5	1091.5	1088.1	1084.7	1081.3	1077.9	1076.2	1076.5
150°	1120.6	1119.4	1118.2	1117.0	1115.8	1112.6	1109.4	1106.2	1103.0	1101.4	1102.1
152.5°	1143.1	1141.9	1140.7	1139.5	1138.3	1135.3	1132.3	1129.3	1126.3	1124.8	1125.6
155°	1162.9	1161.7	1160.5	1159.3	1158.1	1155.7	1153.3	1150.9	1148.5	1147.3	1148.2
157.5°	1180.7	1179.3	1177.9	1176.5	1175.1	1173.3	1171.5	1169.8	1168.0	1167.1	1167.9
160°	1195.2	1194.0	1192.8	1191.6	1190.4	1189.2	1188.0	1186.8	1185.6	1185.0	1185.6
162.5°	1209.5	1208.1	1206.7	1205.3	1203.9	1202.9	1201.9	1200.9	1199.9	1199.4	1200.0
165°	1220.3	1218.9	1217.5	1216.1	1214.7	1214.1	1213.5	1212.9	1212.3	1212.0	1212.6
167.5°	1230.2	1228.8	1227.4	1226.0	1224.6	1224.0	1223.4	1222.8	1222.2	1221.9	1222.5
170°	1237.4	1236.0	1234.6	1233.2	1231.8	1231.4	1231.0	1230.6	1230.2	1230.0	1230.6
172.5°	1242.8	1241.4	1240.0	1238.6	1237.2	1236.8	1236.4	1236.0	1235.6	1235.4	1236.0
175°	1246.4	1245.0	1243.6	1242.2	1240.8	1240.4	1240.0	1239.6	1239.2	1239.0	1239.7
177.5°	1247.3	1245.9	1244.5	1243.1	1241.7	1241.5	1241.3	1241.1	1240.9	1240.8	1241.5
180°	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6

TEST NUMBER: P1009938

CATALOG NUMBER: S122RDIP-B290D925UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	632.5	632.5	632.5	632.5
2.5°	621.1	619.7	627.6	636.4
5°	608.3	610.5	620.6	632.9
7.5°	595.1	600.0	611.8	628.1
10°	576.7	585.4	603.5	620.2
12.5°	558.6	570.5	587.6	607.4
15°	538.4	551.6	572.7	596.4
17.5°	516.0	530.9	555.6	581.5
20°	492.3	512.0	538.0	566.1
22.5°	465.9	489.6	516.4	547.6
25°	440.4	466.3	493.1	529.2
27.5°	415.4	440.8	470.7	507.2
30°	390.3	413.6	445.7	484.8
32.5°	363.5	387.7	421.5	461.5
35°	338.9	363.0	394.7	434.3
37.5°	312.5	338.4	368.8	409.6
40°	281.7	312.1	341.5	380.6
42.5°	256.2	288.3	316.9	353.8
45°	236.0	266.4	290.1	326.1
47.5°	217.1	241.7	265.9	299.3
50°	199.1	218.0	243.1	272.9
52.5°	180.6	196.9	218.4	246.6
55°	163.9	179.3	198.7	220.2
57.5°	148.6	159.5	178.9	198.2
60°	131.4	142.8	157.8	174.1
62.5°	116.9	125.7	139.8	153.4
65°	101.5	109.9	120.4	133.2
67.5°	87.5	94.9	103.3	113.4
70°	74.7	80.4	86.6	95.4
72.5°	61.1	67.2	73.0	80.0
75°	50.1	52.7	57.6	62.4
77.5°	38.7	42.2	44.8	48.8
80°	27.7	30.8	31.6	34.7
82.5°	18.5	20.2	22.0	22.9
85°	10.5	11.4	13.2	13.6
87.5°	4.0	4.4	5.3	6.2
90°	7.5	5.3	3.1	0.9
92.5°	20.1	20.9	21.7	22.5
95°	38.7	45.2	51.8	58.4
97.5°	56.1	72.4	88.8	105.2
100°	77.0	104.4	131.7	159.1
102.5°	217.3	217.7	218.1	218.5
105°	291.3	285.3	279.3	273.3
107.5°	352.1	347.2	342.2	337.2
110°	410.9	406.7	402.5	398.3

TEST NUMBER: P1009938

CATALOG NUMBER: S122RDIP-B290D925UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	466.6	463.1	459.5	455.9
115°	527.2	523.8	520.4	517.0
117.5°	582.0	578.0	574.0	570.0
120°	638.4	635.4	632.4	629.4
122.5°	689.3	686.1	682.9	679.7
125°	738.8	736.2	733.6	731.0
127.5°	786.1	783.3	780.5	777.7
130°	831.4	828.2	825.0	821.8
132.5°	874.5	872.0	869.4	866.8
135°	914.1	910.9	907.7	904.5
137.5°	951.3	948.9	946.5	944.1
140°	987.5	985.9	984.3	982.7
142.5°	1019.3	1017.9	1016.5	1015.1
145°	1048.7	1048.9	1049.1	1049.3
147.5°	1077.1	1077.7	1078.3	1078.9
150°	1103.5	1104.9	1106.3	1107.7
152.5°	1127.2	1128.8	1130.4	1132.0
155°	1150.0	1151.8	1153.6	1155.4
157.5°	1169.5	1171.0	1172.6	1174.2
160°	1186.8	1188.0	1189.2	1190.4
162.5°	1201.2	1202.4	1203.6	1204.8
165°	1213.8	1215.0	1216.2	1217.4
167.5°	1223.7	1224.9	1226.1	1227.3
170°	1231.8	1233.0	1234.2	1235.4
172.5°	1237.2	1238.4	1239.6	1240.8
175°	1241.1	1242.5	1243.9	1245.3
177.5°	1242.9	1244.3	1245.7	1247.1
180°	1242.6	1242.6	1242.6	1242.6

(END OF REPORT)