

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009985

Luminaire Tested: S122RDIP-B485D330UB30-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009985
REPORT IS A COMBINATION OF REPORTS P988275 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B485D330UB30-4F0-XX-W2A-A1
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3029.0 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009985

CATALOG NUMBER: S122RDIP-B485D330UB30-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1009985

CATALOG NUMBER: S122RDIP-B485D330UB30-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	77	77	77	66	66	66
1	101	97	94	90	95	91	88	85	80	78	76	70	68	66	60	59	58
2	93	86	80	75	87	81	76	72	71	67	64	62	60	57	54	52	50
3	86	77	70	64	80	72	66	61	64	59	55	56	53	50	49	46	44
4	79	69	61	55	74	65	58	53	58	52	48	51	47	43	44	41	39
5	73	62	54	48	68	58	52	46	52	47	42	46	42	38	41	37	35
6	68	56	48	43	63	53	46	41	47	42	38	42	38	34	37	34	31
7	63	51	43	38	59	48	42	37	43	38	34	39	34	31	35	31	28
8	59	47	39	34	55	44	38	33	40	34	30	36	31	28	32	28	26
9	55	43	36	31	52	41	34	30	37	32	28	33	29	26	30	26	24
10	52	40	33	28	48	38	32	27	34	29	25	31	27	24	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16945	16945	16945	16945
5°	16986	17998	17044	14379
10°	16798	19025	16917	11875
15°	16433	19030	16712	8920
20°	15995	15731	16343	7359
25°	15464	9830	15797	6261
30°	14786	6293	15187	5389
35°	13959	4837	14411	4612
40°	13038	4066	13597	4034
45°	12056	3460	12560	3387
50°	11048	2940	11565	2930
55°	9931	2556	10467	2521
60°	8940	1948	9413	1924
65°	8013	1466	8489	1663
70°	6990	1171	7540	1355
75°	5907	898	6450	1026
80°	4694	610	5046	673
85°	3263	315	3574	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 15501 cd/sqm

TEST NUMBER: P1009985

CATALOG NUMBER: S122RDIP-B485D330UB30-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.5	3.4
10°-20°	283.4	9.4
20°-30°	364.8	12.0
30°-40°	346.1	11.4
40°-50°	296.6	9.8
50°-60°	225.9	7.5
60°-70°	142.4	4.7
70°-80°	71.1	2.3
80°-90°	19.5	0.6
90°-100°	26.1	0.9
100°-110°	82.9	2.7
110°-120°	141.8	4.7
120°-130°	186.4	6.2
130°-140°	209.3	6.9
140°-150°	205.2	6.8
150°-160°	172.1	5.7
160°-170°	114.2	3.8
170°-180°	39.9	1.3
0°-30°	749.7	24.8
0°-40°	1095.8	36.2
0°-60°	1618.2	53.4
0°-90°	1851.2	61.1
90°-120°	250.7	8.3
90°-150°	851.6	28.1
90°-180°	1178.0	38.9
0°-180°	3029.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1070	1070	1070	1070	1070	
5°	1071	1191	1075	952	1071	102
15°	1010	1344	1027	630	1010	284
25°	896	717	915	457	896	411
35°	735	353	759	337	735	460
45°	552	246	575	240	552	426
55°	373	170	393	168	373	336
65°	225	88	239	100	225	224
75°	106	47	115	54	106	114
85°	23	13	25	14	23	26
90°	0	12	0	12	0	3
95°	18	22	18	22	18	21
105°	76	79	76	79	76	81
115°	142	142	142	142	142	141
125°	207	208	207	208	207	185
135°	268	271	268	271	268	207
145°	325	328	325	328	325	203
155°	372	374	372	374	372	171
165°	404	405	404	405	404	114
175°	421	419	421	419	421	40
180°	421	421	421	421	421	

TEST NUMBER: P1009985

CATALOG NUMBER: S122RDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1077.2	1081.7	1083.9	1086.9	1093.6	1098.1	1104.7	1106.2	1105.5	1108.5	1100.3
5°	1071.3	1080.9	1089.9	1097.3	1109.2	1116.6	1124.8	1134.5	1136.7	1147.9	1141.2
7.5°	1063.1	1077.2	1089.9	1104.7	1122.6	1132.3	1144.9	1159.8	1166.5	1179.9	1183.6
10°	1049.7	1069.8	1091.4	1107.0	1131.5	1148.6	1160.5	1184.3	1200.0	1220.1	1217.1
12.5°	1028.1	1054.2	1083.2	1109.2	1141.2	1152.4	1174.7	1199.2	1219.3	1237.9	1254.3
15°	1009.5	1039.3	1071.3	1103.3	1139.7	1160.5	1182.9	1214.8	1236.4	1269.2	1283.3
17.5°	984.2	1022.2	1060.1	1095.8	1139.0	1162.8	1190.3	1221.5	1253.5	1284.8	1295.9
20°	958.2	999.1	1040.0	1088.4	1137.5	1160.5	1188.8	1227.5	1258.7	1283.3	1283.3
22.5°	926.9	976.8	1023.7	1069.8	1123.3	1156.8	1185.8	1231.2	1253.5	1258.7	1238.7
25°	895.7	945.5	996.9	1054.2	1115.2	1144.9	1177.7	1220.1	1227.5	1206.7	1154.6
27.5°	858.5	914.3	972.3	1034.1	1098.1	1135.2	1165.0	1193.3	1179.1	1123.3	1042.3
30°	820.6	880.8	946.3	1005.1	1082.4	1116.6	1141.9	1150.1	1105.5	1014.7	909.8
32.5°	781.1	839.9	909.1	979.8	1057.9	1090.6	1107.0	1085.4	1003.6	889.0	761.0
35°	735.0	801.2	873.4	947.0	1024.4	1049.0	1058.6	1005.8	900.9	752.9	625.7
37.5°	693.3	759.6	836.9	912.1	987.2	1000.6	990.9	908.3	775.2	628.6	504.4
40°	644.2	714.9	790.8	874.9	936.6	940.3	916.5	809.4	644.2	506.6	430.0
42.5°	598.9	670.3	746.2	831.7	878.6	865.9	834.0	693.3	537.9	436.7	374.9
45°	552.0	619.7	701.5	777.4	810.9	781.1	732.8	583.2	451.6	375.7	328.1
47.5°	506.6	569.9	650.9	723.9	729.8	696.3	639.0	488.8	391.3	330.3	291.6
50°	462.0	525.2	601.1	661.4	655.4	609.3	544.6	424.8	340.0	291.6	259.6
52.5°	417.3	474.6	548.3	595.9	570.6	526.0	462.0	360.1	296.8	254.4	229.9
55°	372.7	426.3	489.5	528.9	488.8	437.4	392.1	308.7	257.4	223.2	204.6
57.5°	335.5	377.9	435.9	459.8	411.4	371.2	331.8	265.6	223.2	198.6	177.1
60°	294.6	333.3	380.9	395.0	345.2	312.5	279.0	224.7	191.2	169.6	155.5
62.5°	259.6	291.6	328.1	328.1	284.2	259.6	234.3	188.2	160.7	143.6	136.9
65°	225.4	248.5	274.5	271.5	234.3	212.8	192.7	155.5	134.7	122.7	116.1
67.5°	191.9	209.8	226.9	216.5	189.7	171.1	152.5	125.7	111.6	103.4	94.5
70°	161.4	175.6	184.5	174.8	148.0	132.4	119.0	101.2	90.0	79.6	74.4
72.5°	135.4	141.3	144.3	132.4	110.1	101.2	91.5	78.9	69.2	64.0	62.5
75°	105.6	110.8	108.6	99.7	81.1	74.4	67.0	58.0	55.8	52.8	51.3
77.5°	82.6	82.6	78.9	70.7	58.0	52.8	49.8	45.4	43.1	42.4	40.9
80°	58.8	58.0	55.8	46.9	39.4	36.5	36.5	33.5	32.7	31.2	31.2
82.5°	38.7	38.7	35.7	28.3	26.0	25.3	24.5	23.1	23.1	22.3	22.3
85°	23.1	21.6	17.9	15.6	14.9	14.9	14.1	13.4	14.1	13.4	13.4
87.5°	10.4	8.2	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
90°	0.4	1.3	2.3	3.2	4.1	4.6	5.5	7.2	8.9	10.7	12.4
92.5°	7.8	8.4	9.1	9.7	10.4	10.7	10.7	10.8	10.9	10.9	11.0
95°	18.5	19.3	20.1	20.8	21.6	22.0	22.1	22.3	22.4	22.6	22.8
97.5°	30.9	31.6	32.3	33.0	33.7	34.1	34.3	34.6	34.9	35.3	35.6
100°	45.1	45.7	46.4	47.0	47.7	48.0	48.1	48.4	48.6	48.9	49.1
102.5°	60.1	60.6	61.0	61.5	62.0	62.2	62.4	62.7	63.0	63.3	63.6
105°	76.4	76.6	76.9	77.1	77.4	77.5	77.6	77.7	77.9	78.0	78.2
107.5°	92.8	93.1	93.4	93.7	94.0	94.2	94.2	94.2	94.2	94.2	94.2
110°	108.4	108.9	109.4	109.9	110.4	110.6	110.6	110.6	110.6	110.6	110.6

TEST NUMBER: P1009985

CATALOG NUMBER: S122RDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	125.5	126.0	126.4	126.9	127.4	127.6	127.6	127.5	127.4	127.4	127.3
115°	142.2	142.7	143.1	143.6	144.1	144.3	144.2	144.1	143.9	143.8	143.6
117.5°	158.9	159.5	160.2	160.8	161.5	161.8	161.6	161.2	160.8	160.4	160.0
120°	175.6	176.2	176.9	177.5	178.2	178.5	178.2	177.5	176.9	176.2	175.6
122.5°	190.9	191.7	192.5	193.3	194.1	194.5	194.3	193.9	193.5	193.1	192.7
125°	206.9	207.6	208.3	209.0	209.7	210.1	210.0	209.7	209.5	209.2	209.0
127.5°	222.5	223.4	224.3	225.2	226.1	226.5	226.3	226.0	225.7	225.3	225.0
130°	237.1	238.1	239.1	240.2	241.2	241.7	241.6	241.5	241.3	241.2	241.0
132.5°	253.5	254.3	255.1	255.8	256.6	257.0	257.0	257.1	257.2	257.3	257.4
135°	267.7	268.6	269.4	270.3	271.2	271.6	271.7	271.8	272.0	272.1	272.3
137.5°	283.3	284.0	284.7	285.4	286.1	286.5	286.6	286.7	286.9	287.0	287.2
140°	297.2	297.9	298.6	299.3	300.0	300.4	300.6	301.0	301.4	301.8	302.2
142.5°	311.4	312.1	312.8	313.5	314.2	314.6	314.7	315.0	315.2	315.5	315.7
145°	324.9	325.5	326.0	326.6	327.1	327.4	327.6	328.1	328.6	329.1	329.6
147.5°	337.0	337.7	338.4	339.1	339.8	340.2	340.4	340.7	341.0	341.3	341.6
150°	349.5	350.0	350.4	350.9	351.4	351.6	351.8	352.1	352.4	352.7	353.0
152.5°	360.5	361.0	361.4	361.9	362.4	362.6	362.8	363.2	363.6	364.0	364.4
155°	371.5	371.7	372.0	372.2	372.5	372.6	372.7	372.9	373.2	373.4	373.6
157.5°	381.1	381.3	381.4	381.6	381.7	381.8	381.9	382.0	382.2	382.3	382.5
160°	389.6	389.8	389.9	390.1	390.2	390.3	390.3	390.4	390.5	390.6	390.7
162.5°	397.5	397.5	397.5	397.5	397.5	397.5	397.5	397.6	397.7	397.7	397.8
165°	404.2	404.1	404.1	404.0	403.9	403.9	403.9	403.9	403.9	403.9	403.9
167.5°	410.3	410.1	409.8	409.6	409.3	409.2	409.2	409.2	409.2	409.2	409.2
170°	414.9	414.7	414.4	414.2	413.9	413.8	413.8	413.7	413.6	413.6	413.5
172.5°	418.1	417.9	417.6	417.4	417.1	417.0	417.0	416.9	416.8	416.8	416.7
175°	420.6	420.4	420.1	419.9	419.6	419.5	419.4	419.3	419.1	419.0	418.8
177.5°	422.0	421.8	421.5	421.3	421.0	420.9	420.8	420.7	420.5	420.4	420.2
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3

TEST NUMBER: P1009985

CATALOG NUMBER: S122RDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1108.5	1110.0	1112.2	1122.6	1124.1	1127.1	1125.6	1125.6	1126.3	1124.8	1125.6
5°	1156.1	1158.3	1169.5	1182.1	1185.1	1182.1	1185.8	1191.0	1191.0	1191.0	1189.6
7.5°	1200.7	1208.9	1221.5	1240.1	1243.9	1247.6	1254.3	1249.8	1251.3	1258.0	1255.8
10°	1243.9	1255.8	1269.9	1285.5	1293.7	1298.9	1301.9	1308.6	1324.2	1306.4	1313.0
12.5°	1284.8	1301.9	1316.8	1333.9	1339.8	1346.5	1348.8	1354.7	1354.7	1354.0	1359.2
15°	1311.6	1327.2	1340.6	1351.7	1353.2	1351.7	1350.2	1351.0	1353.2	1344.3	1349.5
17.5°	1317.5	1319.0	1323.5	1319.0	1319.7	1304.1	1295.2	1293.0	1272.1	1272.9	1290.0
20°	1288.5	1263.2	1256.5	1232.0	1217.1	1176.9	1175.4	1164.3	1120.4	1133.8	1130.8
22.5°	1208.9	1165.7	1108.5	1080.2	1066.1	1023.7	990.9	967.9	952.2	936.6	929.9
25°	1104.0	1034.1	953.0	897.2	889.0	849.6	789.3	761.0	727.6	717.2	735.0
27.5°	968.6	877.8	786.3	700.8	685.2	649.5	619.0	598.9	560.2	558.0	559.4
30°	784.9	693.3	616.7	560.9	522.2	505.9	485.8	470.9	455.3	461.2	462.7
32.5°	645.0	558.0	486.5	456.8	438.9	428.5	411.4	401.7	395.0	392.8	392.1
35°	512.6	454.5	422.6	393.5	383.1	375.7	363.0	358.6	352.6	353.4	353.4
37.5°	438.9	390.6	366.8	351.9	342.2	338.5	330.3	325.8	322.1	320.6	322.9
40°	378.7	345.2	330.3	316.9	308.7	307.2	302.8	297.6	293.1	293.9	296.1
42.5°	334.8	315.4	297.6	287.2	281.2	279.0	275.3	271.5	271.5	269.3	268.6
45°	299.8	284.2	269.3	259.6	255.9	252.9	248.5	247.7	244.8	245.5	246.2
47.5°	268.6	255.9	244.8	235.1	231.4	230.6	226.2	223.2	223.2	222.4	221.7
50°	240.3	227.6	218.0	212.8	207.6	206.1	205.3	204.6	203.1	203.1	203.8
52.5°	217.2	204.6	197.1	192.7	189.7	188.2	188.2	187.5	187.5	187.5	186.7
55°	191.9	181.5	175.6	174.1	172.6	171.8	171.1	169.6	168.9	170.4	168.9
57.5°	168.1	164.4	159.2	157.7	154.0	154.0	151.8	150.3	148.8	150.3	150.3
60°	149.5	144.3	141.3	136.9	133.9	130.9	127.2	126.5	125.0	124.2	123.5
62.5°	130.2	125.7	118.3	111.6	107.1	104.2	102.7	101.9	101.9	101.2	101.2
65°	108.6	98.2	94.5	92.2	91.5	90.8	89.3	88.5	89.3	88.5	89.3
67.5°	84.8	83.3	81.1	79.6	78.9	78.1	78.1	77.4	77.4	77.4	77.4
70°	73.6	69.9	69.2	67.7	67.7	67.0	67.0	67.0	67.0	66.2	67.7
72.5°	61.0	58.8	58.0	57.3	57.3	57.3	56.5	56.5	56.5	55.8	56.5
75°	49.8	49.1	47.6	47.6	46.9	47.6	46.9	46.9	46.1	46.9	46.9
77.5°	40.2	39.4	38.7	38.7	37.9	37.9	37.9	37.9	37.9	37.9	38.7
80°	30.5	29.8	29.0	29.8	29.0	29.8	29.0	29.0	29.8	29.0	29.0
82.5°	22.3	21.6	21.6	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8
85°	13.4	12.6	12.6	13.4	12.6	13.4	12.6	12.6	12.6	13.4	13.4
87.5°	6.0	6.7	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.7
90°	12.2	12.1	11.9	11.8	11.7	11.7	11.8	11.9	12.0	12.1	12.0
92.5°	11.1	11.2	11.3	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4
95°	22.8	22.8	22.8	22.8	22.8	22.7	22.5	22.4	22.2	22.0	22.2
97.5°	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6
100°	49.1	49.1	49.1	49.1	49.1	49.1	49.0	48.9	48.8	48.7	48.8
102.5°	63.7	63.8	63.9	64.0	64.0	64.0	63.9	63.8	63.7	63.6	63.7
105°	78.4	78.5	78.7	78.8	78.9	78.9	78.9	78.9	78.9	78.9	78.9
107.5°	94.3	94.4	94.5	94.6	94.6	94.4	94.0	93.6	93.2	92.8	93.2
110°	110.6	110.6	110.6	110.6	110.6	110.5	110.2	110.0	109.7	109.5	109.7

TEST NUMBER: P1009985

CATALOG NUMBER: S122RDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	127.1	126.8	126.6	126.3	126.2	126.1	126.0	125.8	125.7	125.5	125.7
115°	143.5	143.5	143.4	143.3	143.3	143.2	142.9	142.7	142.4	142.2	142.4
117.5°	159.8	159.5	159.3	159.0	158.9	158.8	158.5	158.3	158.0	157.8	158.0
120°	175.6	175.6	175.6	175.6	175.6	175.5	175.3	175.0	174.8	174.6	174.8
122.5°	192.5	192.2	192.0	191.7	191.6	191.5	191.4	191.2	191.1	190.9	191.1
125°	208.8	208.6	208.3	208.1	208.0	208.0	207.9	207.8	207.7	207.6	207.7
127.5°	224.7	224.4	224.1	223.8	223.6	223.5	223.2	223.0	222.7	222.5	222.7
130°	240.8	240.7	240.5	240.4	240.3	240.1	239.8	239.5	239.2	238.9	239.2
132.5°	257.0	256.6	256.2	255.8	255.6	255.5	255.2	255.0	254.7	254.5	254.7
135°	272.2	272.2	272.1	272.0	272.0	271.9	271.6	271.4	271.1	270.9	271.1
137.5°	287.1	287.1	287.0	286.9	286.9	286.7	286.4	286.1	285.8	285.5	285.8
140°	302.2	302.2	302.2	302.2	302.2	302.0	301.7	301.4	301.1	300.8	301.1
142.5°	315.8	315.8	315.9	316.0	316.0	315.8	315.5	315.2	314.9	314.6	314.9
145°	329.7	329.7	329.8	329.9	329.9	329.7	329.4	329.1	328.8	328.5	328.8
147.5°	341.8	342.0	342.1	342.3	342.4	342.2	341.9	341.6	341.2	340.9	341.2
150°	353.2	353.5	353.7	354.0	354.1	354.0	353.7	353.5	353.2	353.0	353.2
152.5°	364.7	365.0	365.3	365.6	365.8	365.6	365.3	365.0	364.7	364.4	364.7
155°	374.0	374.4	374.8	375.2	375.4	375.3	375.0	374.8	374.5	374.3	374.5
157.5°	383.1	383.6	384.2	384.7	385.0	384.8	384.4	384.0	383.6	383.2	383.6
160°	391.2	391.6	392.1	392.6	392.8	392.6	392.3	392.0	391.7	391.4	391.7
162.5°	398.4	398.9	399.5	400.0	400.3	400.1	399.7	399.3	398.9	398.5	398.9
165°	404.4	405.0	405.5	406.0	406.3	406.1	405.7	405.4	405.0	404.6	405.0
167.5°	409.8	410.3	410.9	411.4	411.7	411.5	411.1	410.7	410.3	409.9	410.3
170°	414.0	414.6	415.1	415.6	415.9	415.7	415.2	414.7	414.3	413.8	414.3
172.5°	417.2	417.8	418.3	418.8	419.1	418.9	418.4	417.9	417.5	417.0	417.5
175°	419.4	419.9	420.5	421.0	421.3	421.1	420.6	420.1	419.6	419.1	419.6
177.5°	420.7	421.1	421.6	422.1	422.3	422.1	421.6	421.1	420.7	420.2	420.7
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3

TEST NUMBER: P1009985

CATALOG NUMBER: S122RDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1128.6	1123.3	1121.9	1123.3	1121.9	1122.6	1117.4	1098.1	1103.3	1095.1	1099.5
5°	1192.5	1188.1	1178.4	1176.9	1175.4	1173.9	1166.5	1149.4	1142.7	1131.5	1130.8
7.5°	1253.5	1253.5	1246.1	1240.9	1234.2	1229.0	1219.3	1194.0	1183.6	1170.2	1162.8
10°	1313.8	1294.4	1302.6	1297.4	1281.1	1278.1	1260.2	1245.4	1225.3	1211.9	1200.0
12.5°	1356.9	1351.0	1343.5	1339.1	1334.6	1325.0	1313.0	1275.1	1264.7	1237.9	1224.5
15°	1355.5	1351.7	1354.0	1354.0	1352.5	1350.2	1340.6	1313.0	1295.2	1269.2	1246.1
17.5°	1282.5	1292.2	1301.9	1308.6	1323.5	1330.2	1339.1	1322.7	1311.6	1289.2	1264.7
20°	1155.3	1179.1	1207.4	1213.4	1226.8	1266.2	1284.0	1298.2	1302.6	1295.2	1275.1
22.5°	978.3	998.4	1066.8	1065.3	1084.7	1131.5	1183.6	1226.0	1259.5	1278.1	1270.6
25°	766.3	794.5	831.0	858.5	921.7	991.7	1056.4	1124.1	1182.1	1233.4	1246.1
27.5°	579.5	616.7	645.7	682.2	714.2	796.8	880.1	985.7	1053.4	1150.9	1201.5
30°	468.7	485.8	514.8	531.9	547.5	610.8	705.3	809.4	928.4	1040.8	1127.8
32.5°	400.2	412.1	433.7	441.2	457.5	499.9	559.4	654.7	777.4	913.6	1028.1
35°	359.3	372.0	376.4	383.1	396.5	423.3	464.2	533.4	644.2	777.4	914.3
37.5°	324.4	331.1	343.7	348.2	352.6	372.7	400.2	448.6	522.2	631.6	783.4
40°	299.8	303.5	310.2	313.9	316.9	331.1	355.6	388.3	442.6	526.0	665.8
42.5°	273.8	278.2	282.7	287.2	290.9	302.0	316.9	348.2	384.6	447.8	549.0
45°	248.5	251.5	256.7	259.6	264.8	273.8	287.2	308.7	341.5	381.6	463.5
47.5°	225.4	229.1	231.4	235.1	238.8	248.5	261.1	275.3	302.0	341.5	401.0
50°	204.6	209.0	212.0	212.8	215.7	224.7	235.1	250.7	267.8	298.3	350.4
52.5°	189.7	190.4	192.7	195.7	194.9	200.1	209.8	221.7	239.5	264.1	302.0
55°	172.6	174.8	176.3	177.1	177.1	181.5	186.7	197.9	212.0	232.1	264.1
57.5°	151.0	153.3	157.7	159.2	161.4	163.7	165.9	173.3	185.2	204.6	230.6
60°	128.7	130.2	134.7	137.6	139.1	145.1	148.0	154.0	160.7	174.8	199.4
62.5°	103.4	104.9	107.1	110.1	113.1	122.0	129.4	135.4	140.6	150.3	170.4
65°	90.0	90.8	92.2	93.0	93.7	97.5	104.2	112.3	122.0	129.4	141.3
67.5°	78.1	78.9	79.6	81.1	81.8	82.6	85.6	87.8	97.5	107.9	116.8
70°	67.0	68.4	69.2	69.2	69.9	71.4	72.9	75.9	78.9	84.1	95.2
72.5°	56.5	57.3	58.8	58.8	58.8	60.3	61.7	63.2	64.7	67.7	72.2
75°	46.9	48.4	48.4	48.4	49.1	49.1	50.6	52.1	53.6	55.8	57.3
77.5°	38.7	38.7	38.7	38.7	39.4	39.4	40.2	41.7	42.4	43.1	44.6
80°	29.0	29.8	29.8	29.8	30.5	30.5	30.5	32.0	32.7	32.7	34.2
82.5°	21.6	21.6	21.6	22.3	21.6	22.3	22.3	23.1	22.3	23.1	23.8
85°	13.4	13.4	13.4	14.1	14.1	14.1	14.1	14.1	14.1	14.1	14.9
87.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	7.4	6.7	6.7
90°	11.9	11.8	11.7	11.7	11.8	11.9	12.1	12.2	12.4	10.7	8.9
92.5°	11.4	11.4	11.4	11.4	11.4	11.3	11.2	11.1	11.0	10.9	10.9
95°	22.4	22.5	22.7	22.8	22.8	22.8	22.8	22.8	22.8	22.6	22.4
97.5°	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.3	34.9
100°	48.9	49.0	49.1	49.1	49.1	49.1	49.1	49.1	49.1	48.9	48.6
102.5°	63.8	63.9	64.0	64.0	64.0	63.9	63.8	63.7	63.6	63.3	63.0
105°	78.9	78.9	78.9	78.9	78.8	78.7	78.5	78.4	78.2	78.0	77.9
107.5°	93.6	94.0	94.4	94.6	94.6	94.5	94.4	94.3	94.2	94.2	94.2
110°	110.0	110.2	110.5	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.6

TEST NUMBER: P1009985

CATALOG NUMBER: S122RDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	125.8	126.0	126.1	126.2	126.3	126.6	126.8	127.1	127.3	127.4	127.4
115°	142.7	142.9	143.2	143.3	143.3	143.4	143.5	143.5	143.6	143.8	143.9
117.5°	158.3	158.5	158.8	158.9	159.0	159.3	159.5	159.8	160.0	160.4	160.8
120°	175.0	175.3	175.5	175.6	175.6	175.6	175.6	175.6	175.6	176.2	176.9
122.5°	191.2	191.4	191.5	191.6	191.7	192.0	192.2	192.5	192.7	193.1	193.5
125°	207.8	207.9	208.0	208.0	208.1	208.3	208.6	208.8	209.0	209.2	209.5
127.5°	223.0	223.2	223.5	223.6	223.8	224.1	224.4	224.7	225.0	225.3	225.7
130°	239.5	239.8	240.1	240.3	240.4	240.5	240.7	240.8	241.0	241.2	241.3
132.5°	255.0	255.2	255.5	255.6	255.8	256.2	256.6	257.0	257.4	257.3	257.2
135°	271.4	271.6	271.9	272.0	272.0	272.1	272.2	272.2	272.3	272.1	272.0
137.5°	286.1	286.4	286.7	286.9	286.9	287.0	287.1	287.1	287.2	287.0	286.9
140°	301.4	301.7	302.0	302.2	302.2	302.2	302.2	302.2	302.2	301.8	301.4
142.5°	315.2	315.5	315.8	316.0	316.0	315.9	315.8	315.8	315.7	315.5	315.2
145°	329.1	329.4	329.7	329.9	329.9	329.8	329.7	329.7	329.6	329.1	328.6
147.5°	341.6	341.9	342.2	342.4	342.3	342.1	342.0	341.8	341.6	341.3	341.0
150°	353.5	353.7	354.0	354.1	354.0	353.7	353.5	353.2	353.0	352.7	352.4
152.5°	365.0	365.3	365.6	365.8	365.6	365.3	365.0	364.7	364.4	364.0	363.6
155°	374.8	375.0	375.3	375.4	375.2	374.8	374.4	374.0	373.6	373.4	373.2
157.5°	384.0	384.4	384.8	385.0	384.7	384.2	383.6	383.1	382.5	382.3	382.2
160°	392.0	392.3	392.6	392.8	392.6	392.1	391.6	391.2	390.7	390.6	390.5
162.5°	399.3	399.7	400.1	400.3	400.0	399.5	398.9	398.4	397.8	397.7	397.7
165°	405.4	405.7	406.1	406.3	406.0	405.5	405.0	404.4	403.9	403.9	403.9
167.5°	410.7	411.1	411.5	411.7	411.4	410.9	410.3	409.8	409.2	409.2	409.2
170°	414.7	415.2	415.7	415.9	415.6	415.1	414.6	414.0	413.5	413.6	413.6
172.5°	417.9	418.4	418.9	419.1	418.8	418.3	417.8	417.2	416.7	416.8	416.8
175°	420.1	420.6	421.1	421.3	421.0	420.5	419.9	419.4	418.8	419.0	419.1
177.5°	421.1	421.6	422.1	422.3	422.1	421.6	421.1	420.7	420.2	420.4	420.5
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3

TEST NUMBER: P1009985

CATALOG NUMBER: S122RDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1092.8	1089.1	1089.1	1086.9	1086.9	1075.0	1075.0	1078.7	1074.2	1069.0	1061.6
5°	1121.1	1112.9	1110.7	1107.7	1098.1	1083.2	1077.2	1075.0	1066.1	1054.9	1042.3
7.5°	1147.9	1134.5	1127.8	1121.1	1108.5	1087.6	1075.7	1067.5	1054.2	1037.0	1020.7
10°	1173.9	1156.8	1139.7	1131.5	1113.7	1087.6	1070.5	1057.1	1037.8	1014.7	991.7
12.5°	1197.7	1162.0	1159.1	1142.7	1116.6	1086.9	1060.9	1041.5	1017.0	990.2	963.4
15°	1218.6	1182.1	1164.3	1149.4	1115.2	1078.0	1050.4	1026.6	993.9	963.4	930.7
17.5°	1229.0	1189.6	1177.7	1153.1	1118.1	1069.8	1032.6	1003.6	967.9	931.4	894.2
20°	1239.4	1193.3	1173.9	1156.8	1109.2	1054.2	1012.5	979.0	939.6	896.4	855.5
22.5°	1244.6	1193.3	1170.2	1146.4	1100.3	1037.0	987.9	948.5	902.4	858.5	809.4
25°	1235.7	1188.8	1161.3	1136.7	1084.7	1016.2	959.7	915.0	865.9	816.1	766.3
27.5°	1213.4	1178.4	1146.4	1121.1	1063.1	989.4	929.9	879.3	828.7	773.0	722.4
30°	1171.7	1156.1	1130.8	1102.5	1039.3	965.6	895.0	842.9	787.1	731.3	678.5
32.5°	1107.0	1120.4	1104.0	1079.5	1011.0	932.9	857.8	804.9	743.9	683.7	635.3
35°	1028.1	1075.7	1066.8	1049.7	981.3	897.9	822.8	758.8	697.8	636.8	588.5
37.5°	941.8	1014.0	1021.4	1011.0	947.0	862.2	779.6	717.2	654.7	592.9	543.8
40°	823.5	934.4	958.2	962.7	911.3	819.1	732.8	671.8	610.0	549.8	490.3
42.5°	714.9	854.8	884.5	903.1	865.9	776.7	689.6	621.9	560.9	506.6	447.1
45°	613.0	758.8	807.2	831.0	814.6	728.3	638.3	575.1	519.3	469.4	412.1
47.5°	508.1	654.7	722.4	760.3	760.3	679.2	589.2	526.7	473.1	430.7	380.2
50°	438.2	560.2	630.1	680.0	693.3	629.4	544.6	483.6	433.0	386.8	348.2
52.5°	373.5	482.8	540.8	592.9	631.6	575.8	494.7	439.7	389.8	346.7	316.2
55°	322.9	404.7	457.5	514.8	558.0	521.5	446.4	392.8	349.7	313.9	287.9
57.5°	274.5	345.9	389.1	439.7	485.8	458.3	398.0	351.9	313.9	282.7	259.6
60°	233.6	291.6	325.1	364.5	421.8	402.5	352.6	310.2	279.7	251.5	232.1
62.5°	198.6	244.8	273.0	301.3	353.4	344.4	305.8	273.0	247.0	223.2	206.8
65°	162.9	200.9	223.2	247.7	289.4	293.1	261.9	238.8	215.0	194.2	179.3
67.5°	131.7	161.4	181.5	202.4	235.8	246.2	224.7	205.3	185.2	168.1	154.7
70°	106.4	127.2	142.1	158.5	186.0	198.6	187.5	174.1	157.7	143.6	131.7
72.5°	84.1	97.5	106.4	119.0	141.3	154.0	153.3	141.3	129.4	119.8	110.1
75°	61.7	72.2	79.6	87.8	105.6	117.5	120.5	115.3	103.4	96.0	88.5
77.5°	46.9	52.8	56.5	62.5	75.1	85.6	90.0	88.5	80.3	74.4	69.2
80°	35.7	37.2	38.7	40.9	51.3	61.0	64.0	63.2	58.8	56.5	50.6
82.5°	25.3	26.0	26.8	27.5	31.2	39.4	42.4	43.9	40.2	37.9	32.7
85°	14.9	15.6	15.6	17.1	17.9	20.1	25.3	25.3	24.5	21.6	20.8
87.5°	7.4	7.4	6.7	6.7	7.4	8.2	9.7	11.2	9.7	8.9	8.2
90°	7.2	5.5	4.6	4.1	3.2	2.3	1.3	0.4	1.3	2.3	3.2
92.5°	10.8	10.7	10.7	10.4	9.7	9.1	8.4	7.8	8.4	9.1	9.7
95°	22.3	22.1	22.0	21.6	20.8	20.1	19.3	18.5	19.3	20.1	20.8
97.5°	34.6	34.3	34.1	33.7	33.0	32.3	31.6	30.9	31.6	32.3	33.0
100°	48.4	48.1	48.0	47.7	47.0	46.4	45.7	45.1	45.7	46.4	47.0
102.5°	62.7	62.4	62.2	62.0	61.5	61.0	60.6	60.1	60.6	61.0	61.5
105°	77.7	77.6	77.5	77.4	77.1	76.9	76.6	76.4	76.6	76.9	77.1
107.5°	94.2	94.2	94.2	94.0	93.7	93.4	93.1	92.8	93.1	93.4	93.7
110°	110.6	110.6	110.6	110.4	109.9	109.4	108.9	108.4	108.9	109.4	109.9

TEST NUMBER: P1009985

CATALOG NUMBER: S122RDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	127.5	127.6	127.6	127.4	126.9	126.4	126.0	125.5	126.0	126.4	126.9
115°	144.1	144.2	144.3	144.1	143.6	143.1	142.7	142.2	142.7	143.1	143.6
117.5°	161.2	161.6	161.8	161.5	160.8	160.2	159.5	158.9	159.5	160.2	160.8
120°	177.5	178.2	178.5	178.2	177.5	176.9	176.2	175.6	176.2	176.9	177.5
122.5°	193.9	194.3	194.5	194.1	193.3	192.5	191.7	190.9	191.7	192.5	193.3
125°	209.7	210.0	210.1	209.7	209.0	208.3	207.6	206.9	207.6	208.3	209.0
127.5°	226.0	226.3	226.5	226.1	225.2	224.3	223.4	222.5	223.4	224.3	225.2
130°	241.5	241.6	241.7	241.2	240.2	239.1	238.1	237.1	238.1	239.1	240.2
132.5°	257.1	257.0	257.0	256.6	255.8	255.1	254.3	253.5	254.3	255.1	255.8
135°	271.8	271.7	271.6	271.2	270.3	269.4	268.6	267.7	268.6	269.4	270.3
137.5°	286.7	286.6	286.5	286.1	285.4	284.7	284.0	283.3	284.0	284.7	285.4
140°	301.0	300.6	300.4	300.0	299.3	298.6	297.9	297.2	297.9	298.6	299.3
142.5°	315.0	314.7	314.6	314.2	313.5	312.8	312.1	311.4	312.1	312.8	313.5
145°	328.1	327.6	327.4	327.1	326.6	326.0	325.5	324.9	325.5	326.0	326.6
147.5°	340.7	340.4	340.2	339.8	339.1	338.4	337.7	337.0	337.7	338.4	339.1
150°	352.1	351.8	351.6	351.4	350.9	350.4	350.0	349.5	350.0	350.4	350.9
152.5°	363.2	362.8	362.6	362.4	361.9	361.4	361.0	360.5	361.0	361.4	361.9
155°	372.9	372.7	372.6	372.5	372.2	372.0	371.7	371.5	371.7	372.0	372.2
157.5°	382.0	381.9	381.8	381.7	381.6	381.4	381.3	381.1	381.3	381.4	381.6
160°	390.4	390.3	390.3	390.2	390.1	389.9	389.8	389.6	389.8	389.9	390.1
162.5°	397.6	397.5	397.5	397.5	397.5	397.5	397.5	397.5	397.5	397.5	397.5
165°	403.9	403.9	403.9	403.9	404.0	404.1	404.1	404.2	404.1	404.1	404.0
167.5°	409.2	409.2	409.2	409.3	409.6	409.8	410.1	410.3	410.1	409.8	409.6
170°	413.7	413.8	413.8	413.9	414.2	414.4	414.7	414.9	414.7	414.4	414.2
172.5°	416.9	417.0	417.0	417.1	417.4	417.6	417.9	418.1	417.9	417.6	417.4
175°	419.3	419.4	419.5	419.6	419.9	420.1	420.4	420.6	420.4	420.1	419.9
177.5°	420.7	420.8	420.9	421.0	421.3	421.5	421.8	422.0	421.8	421.5	421.3
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3

TEST NUMBER: P1009985

CATALOG NUMBER: S122RDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1058.6	1059.4	1061.6	1054.9	1044.5	1040.0	1026.6	1024.4	1022.2	1022.2	1024.4
5°	1034.8	1031.8	1032.6	1019.9	1005.1	996.1	977.5	980.5	970.8	964.9	966.4
7.5°	1008.8	1000.6	999.9	983.5	964.9	948.5	929.2	924.7	915.8	905.4	900.9
10°	976.0	970.1	958.9	940.3	916.5	903.1	877.1	861.5	859.2	843.6	837.7
12.5°	942.6	932.2	921.0	895.0	868.2	846.6	827.3	810.1	798.2	784.9	775.9
15°	903.9	891.2	878.6	851.1	819.8	798.2	769.2	743.9	709.0	681.4	665.8
17.5°	861.5	847.3	830.2	799.7	769.2	739.5	685.9	656.2	631.6	615.2	605.6
20°	817.6	802.0	784.9	754.4	701.5	649.5	619.7	596.6	581.8	565.4	553.5
22.5°	771.5	755.1	736.5	688.9	633.1	596.6	573.6	552.0	530.4	521.5	515.5
25°	728.3	713.4	689.6	624.9	581.0	547.5	521.5	507.4	496.2	484.3	473.1
27.5°	683.7	656.2	622.7	568.4	540.8	506.6	488.0	477.6	458.3	450.1	444.9
30°	630.1	599.6	567.6	528.9	496.9	473.1	456.0	438.9	427.8	419.6	410.7
32.5°	575.8	546.8	526.7	486.5	462.7	438.2	421.8	411.4	395.0	389.8	386.1
35°	528.9	504.4	486.5	453.8	431.5	409.2	397.3	381.6	371.2	361.6	355.6
37.5°	482.8	469.4	450.8	423.3	399.5	381.6	365.3	360.1	345.9	340.7	334.8
40°	450.8	430.7	415.1	391.3	371.2	351.9	341.5	329.6	319.9	311.7	309.5
42.5°	412.1	397.3	388.3	362.3	341.5	330.3	317.7	304.3	296.8	290.1	282.0
45°	383.1	369.7	357.1	336.3	317.7	303.5	292.4	283.4	270.8	267.8	255.2
47.5°	352.6	339.2	329.6	308.7	291.6	278.2	270.0	258.1	247.7	241.0	235.1
50°	322.1	311.0	302.0	284.2	269.3	255.2	244.0	232.1	227.6	216.5	212.8
52.5°	293.1	285.7	276.0	258.9	244.0	232.1	220.2	210.5	203.8	197.9	193.4
55°	268.6	256.7	252.2	233.6	220.9	208.3	197.9	191.9	183.8	180.0	176.3
57.5°	241.0	234.3	226.9	212.8	198.6	186.7	179.3	170.4	165.9	161.4	158.5
60°	217.2	207.6	201.6	189.7	177.1	165.9	159.2	152.5	146.6	142.8	136.9
62.5°	189.7	182.3	178.5	165.9	155.5	145.1	139.1	132.4	128.0	121.3	113.8
65°	165.9	159.9	155.5	145.1	135.4	125.7	119.8	111.6	105.6	101.9	101.2
67.5°	145.1	140.6	133.9	124.2	114.6	107.1	100.4	93.7	93.0	91.5	91.5
70°	122.0	117.5	113.8	103.4	95.2	87.0	85.6	83.3	81.1	80.3	78.9
72.5°	101.9	98.2	93.7	84.8	76.6	74.4	72.9	71.4	69.2	68.4	67.7
75°	82.6	77.4	74.4	66.2	64.0	62.5	61.0	58.8	57.3	56.5	55.1
77.5°	63.2	58.0	58.0	53.6	52.1	49.8	48.4	46.9	46.1	44.6	44.6
80°	44.6	44.6	43.1	40.9	38.7	37.9	35.7	35.0	34.2	35.0	33.5
82.5°	32.7	29.8	29.8	28.3	26.8	26.0	24.5	24.5	23.8	23.8	23.8
85°	18.6	18.6	17.9	16.4	15.6	15.6	14.9	14.9	14.1	14.1	13.4
87.5°	7.4	6.7	7.4	6.7	6.7	6.0	6.0	6.0	5.2	6.0	5.2
90°	4.1	4.6	5.5	7.2	8.9	10.7	12.4	12.2	12.1	11.9	11.8
92.5°	10.4	10.7	10.7	10.8	10.9	10.9	11.0	11.1	11.2	11.3	11.4
95°	21.6	22.0	22.1	22.3	22.4	22.6	22.8	22.8	22.8	22.8	22.8
97.5°	33.7	34.1	34.3	34.6	34.9	35.3	35.6	35.6	35.6	35.6	35.6
100°	47.7	48.0	48.1	48.4	48.6	48.9	49.1	49.1	49.1	49.1	49.1
102.5°	62.0	62.2	62.4	62.7	63.0	63.3	63.6	63.7	63.8	63.9	64.0
105°	77.4	77.5	77.6	77.7	77.9	78.0	78.2	78.4	78.5	78.7	78.8
107.5°	94.0	94.2	94.2	94.2	94.2	94.2	94.2	94.3	94.4	94.5	94.6
110°	110.4	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.6

TEST NUMBER: P1009985

CATALOG NUMBER: S122RDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	127.4	127.6	127.6	127.5	127.4	127.4	127.3	127.1	126.8	126.6	126.3
115°	144.1	144.3	144.2	144.1	143.9	143.8	143.6	143.5	143.5	143.4	143.3
117.5°	161.5	161.8	161.6	161.2	160.8	160.4	160.0	159.8	159.5	159.3	159.0
120°	178.2	178.5	178.2	177.5	176.9	176.2	175.6	175.6	175.6	175.6	175.6
122.5°	194.1	194.5	194.3	193.9	193.5	193.1	192.7	192.5	192.2	192.0	191.7
125°	209.7	210.1	210.0	209.7	209.5	209.2	209.0	208.8	208.6	208.3	208.1
127.5°	226.1	226.5	226.3	226.0	225.7	225.3	225.0	224.7	224.4	224.1	223.8
130°	241.2	241.7	241.6	241.5	241.3	241.2	241.0	240.8	240.7	240.5	240.4
132.5°	256.6	257.0	257.0	257.1	257.2	257.3	257.4	257.0	256.6	256.2	255.8
135°	271.2	271.6	271.7	271.8	272.0	272.1	272.3	272.2	272.2	272.1	272.0
137.5°	286.1	286.5	286.6	286.7	286.9	287.0	287.2	287.1	287.1	287.0	286.9
140°	300.0	300.4	300.6	301.0	301.4	301.8	302.2	302.2	302.2	302.2	302.2
142.5°	314.2	314.6	314.7	315.0	315.2	315.5	315.7	315.8	315.8	315.9	316.0
145°	327.1	327.4	327.6	328.1	328.6	329.1	329.6	329.7	329.7	329.8	329.9
147.5°	339.8	340.2	340.4	340.7	341.0	341.3	341.6	341.8	342.0	342.1	342.3
150°	351.4	351.6	351.8	352.1	352.4	352.7	353.0	353.2	353.5	353.7	354.0
152.5°	362.4	362.6	362.8	363.2	363.6	364.0	364.4	364.7	365.0	365.3	365.6
155°	372.5	372.6	372.7	372.9	373.2	373.4	373.6	374.0	374.4	374.8	375.2
157.5°	381.7	381.8	381.9	382.0	382.2	382.3	382.5	383.1	383.6	384.2	384.7
160°	390.2	390.3	390.3	390.4	390.5	390.6	390.7	391.2	391.6	392.1	392.6
162.5°	397.5	397.5	397.5	397.6	397.7	397.7	397.8	398.4	398.9	399.5	400.0
165°	403.9	403.9	403.9	403.9	403.9	403.9	403.9	404.4	405.0	405.5	406.0
167.5°	409.3	409.2	409.2	409.2	409.2	409.2	409.2	409.8	410.3	410.9	411.4
170°	413.9	413.8	413.8	413.7	413.6	413.6	413.5	414.0	414.6	415.1	415.6
172.5°	417.1	417.0	417.0	416.9	416.8	416.8	416.7	417.2	417.8	418.3	418.8
175°	419.6	419.5	419.4	419.3	419.1	419.0	418.8	419.4	419.9	420.5	421.0
177.5°	421.0	420.9	420.8	420.7	420.5	420.4	420.2	420.7	421.1	421.6	422.1
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3

TEST NUMBER: P1009985

CATALOG NUMBER: S122RDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1024.4	1022.9	1018.4	1019.9	1017.7	1017.7	1016.2	1016.2	1016.2	1019.9	1017.7
5°	968.6	963.4	958.2	956.0	953.7	951.5	951.5	950.8	957.4	956.0	961.9
7.5°	899.4	897.9	887.5	887.5	883.8	882.3	886.0	886.8	887.5	889.0	892.7
10°	837.7	834.0	819.1	820.6	818.3	815.4	817.6	816.1	821.3	822.8	821.3
12.5°	764.8	758.1	741.7	733.5	724.6	717.9	726.1	720.1	741.0	746.9	763.3
15°	668.1	655.4	644.2	644.2	636.1	630.1	633.8	640.5	645.0	651.7	654.7
17.5°	603.3	598.1	589.2	584.0	581.8	579.5	579.5	582.5	592.2	591.4	597.4
20°	548.3	545.3	540.8	534.1	531.9	530.4	530.4	530.4	537.1	543.1	546.8
22.5°	510.3	508.1	505.1	496.2	491.7	490.3	494.0	496.2	501.4	505.9	509.6
25°	472.4	467.2	462.0	459.0	456.8	456.8	458.3	459.0	461.2	463.5	467.9
27.5°	441.2	437.4	430.0	421.8	421.8	419.6	421.1	422.6	427.8	435.2	438.9
30°	406.2	405.4	402.5	399.5	396.5	395.0	398.0	400.2	401.0	404.7	404.7
32.5°	380.9	375.7	370.5	367.5	366.0	365.3	366.0	369.0	369.0	373.5	378.7
35°	355.6	352.6	347.4	342.2	340.7	337.0	340.0	343.0	348.2	350.4	352.6
37.5°	328.1	324.4	322.1	320.6	317.7	318.4	316.2	320.6	325.1	324.4	325.8
40°	307.2	300.6	293.9	293.1	292.4	291.6	291.6	292.4	295.3	298.3	302.8
42.5°	280.5	278.2	272.3	266.3	264.8	263.4	261.9	264.8	270.8	276.0	278.2
45°	252.9	250.0	248.5	244.0	241.0	240.3	238.8	242.5	247.7	250.0	251.5
47.5°	227.6	226.9	222.4	223.2	220.9	221.7	220.9	223.2	223.2	225.4	226.9
50°	210.5	208.3	206.1	204.6	202.4	202.4	201.6	202.4	205.3	208.3	207.6
52.5°	193.4	189.7	189.0	188.2	186.7	188.2	186.0	186.7	189.7	191.2	190.4
55°	173.3	172.6	171.1	169.6	168.9	168.1	168.1	168.1	171.1	173.3	174.1
57.5°	157.7	154.0	151.0	151.0	148.0	147.3	148.8	149.5	151.8	153.3	154.7
60°	136.1	134.7	130.2	128.0	123.5	122.7	122.7	125.7	129.4	134.7	136.1
62.5°	113.1	110.8	110.1	110.1	110.1	110.1	110.1	110.1	110.1	110.8	110.8
65°	100.4	101.2	100.4	99.7	100.4	100.4	99.7	99.7	99.7	100.4	101.2
67.5°	90.0	89.3	90.0	89.3	88.5	88.5	87.8	88.5	89.3	90.0	90.0
70°	78.1	78.1	77.4	78.1	77.4	76.6	75.9	75.9	77.4	78.1	78.1
72.5°	67.0	67.0	66.2	66.2	64.7	64.7	65.5	64.7	64.7	67.0	67.0
75°	55.8	55.1	54.3	54.3	53.6	53.6	53.6	52.8	54.3	54.3	55.1
77.5°	43.9	43.9	43.9	43.1	43.1	42.4	42.4	43.1	43.1	43.1	43.9
80°	33.5	33.5	33.5	32.7	32.0	32.0	32.0	32.0	32.0	32.7	32.0
82.5°	23.1	23.1	23.1	23.1	23.1	22.3	22.3	22.3	23.1	23.1	22.3
85°	14.1	13.4	14.1	14.1	13.4	14.1	13.4	13.4	12.6	12.6	13.4
87.5°	6.0	5.2	4.5	4.5	5.2	4.5	4.5	4.5	5.2	4.5	4.5
90°	11.7	11.7	11.8	11.9	12.0	12.1	12.0	11.9	11.8	11.7	11.7
92.5°	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4
95°	22.8	22.7	22.5	22.4	22.2	22.0	22.2	22.4	22.5	22.7	22.8
97.5°	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6
100°	49.1	49.1	49.0	48.9	48.8	48.7	48.8	48.9	49.0	49.1	49.1
102.5°	64.0	64.0	63.9	63.8	63.7	63.6	63.7	63.8	63.9	64.0	64.0
105°	78.9	78.9	78.9	78.9	78.9	78.9	78.9	78.9	78.9	78.9	78.9
107.5°	94.6	94.4	94.0	93.6	93.2	92.8	93.2	93.6	94.0	94.4	94.6
110°	110.6	110.5	110.2	110.0	109.7	109.5	109.7	110.0	110.2	110.5	110.6

TEST NUMBER: P1009985

CATALOG NUMBER: S122RDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	126.2	126.1	126.0	125.8	125.7	125.5	125.7	125.8	126.0	126.1	126.2
115°	143.3	143.2	142.9	142.7	142.4	142.2	142.4	142.7	142.9	143.2	143.3
117.5°	158.9	158.8	158.5	158.3	158.0	157.8	158.0	158.3	158.5	158.8	158.9
120°	175.6	175.5	175.3	175.0	174.8	174.6	174.8	175.0	175.3	175.5	175.6
122.5°	191.6	191.5	191.4	191.2	191.1	190.9	191.1	191.2	191.4	191.5	191.6
125°	208.0	208.0	207.9	207.8	207.7	207.6	207.7	207.8	207.9	208.0	208.0
127.5°	223.6	223.5	223.2	223.0	222.7	222.5	222.7	223.0	223.2	223.5	223.6
130°	240.3	240.1	239.8	239.5	239.2	238.9	239.2	239.5	239.8	240.1	240.3
132.5°	255.6	255.5	255.2	255.0	254.7	254.5	254.7	255.0	255.2	255.5	255.6
135°	272.0	271.9	271.6	271.4	271.1	270.9	271.1	271.4	271.6	271.9	272.0
137.5°	286.9	286.7	286.4	286.1	285.8	285.5	285.8	286.1	286.4	286.7	286.9
140°	302.2	302.0	301.7	301.4	301.1	300.8	301.1	301.4	301.7	302.0	302.2
142.5°	316.0	315.8	315.5	315.2	314.9	314.6	314.9	315.2	315.5	315.8	316.0
145°	329.9	329.7	329.4	329.1	328.8	328.5	328.8	329.1	329.4	329.7	329.9
147.5°	342.4	342.2	341.9	341.6	341.2	340.9	341.2	341.6	341.9	342.2	342.4
150°	354.1	354.0	353.7	353.5	353.2	353.0	353.2	353.5	353.7	354.0	354.1
152.5°	365.8	365.6	365.3	365.0	364.7	364.4	364.7	365.0	365.3	365.6	365.8
155°	375.4	375.3	375.0	374.8	374.5	374.3	374.5	374.8	375.0	375.3	375.4
157.5°	385.0	384.8	384.4	384.0	383.6	383.2	383.6	384.0	384.4	384.8	385.0
160°	392.8	392.6	392.3	392.0	391.7	391.4	391.7	392.0	392.3	392.6	392.8
162.5°	400.3	400.1	399.7	399.3	398.9	398.5	398.9	399.3	399.7	400.1	400.3
165°	406.3	406.1	405.7	405.4	405.0	404.6	405.0	405.4	405.7	406.1	406.3
167.5°	411.7	411.5	411.1	410.7	410.3	409.9	410.3	410.7	411.1	411.5	411.7
170°	415.9	415.7	415.2	414.7	414.3	413.8	414.3	414.7	415.2	415.7	415.9
172.5°	419.1	418.9	418.4	417.9	417.5	417.0	417.5	417.9	418.4	418.9	419.1
175°	421.3	421.1	420.6	420.1	419.6	419.1	419.6	420.1	420.6	421.1	421.3
177.5°	422.3	422.1	421.6	421.1	420.7	420.2	420.7	421.1	421.6	422.1	422.3
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3

TEST NUMBER: P1009985

CATALOG NUMBER: S122RDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1019.9	1023.7	1022.2	1014.0	1022.2	1024.4	1028.9	1033.3	1036.3	1040.8	1044.5
5°	956.0	963.4	967.9	963.4	978.3	980.5	990.9	996.9	1005.8	1013.2	1019.2
7.5°	895.7	901.7	910.6	912.1	921.0	931.4	946.3	961.2	975.3	982.7	989.4
10°	831.0	841.4	854.8	851.8	865.2	881.6	897.2	921.0	932.9	946.3	958.2
12.5°	766.3	773.0	790.8	796.8	816.1	828.7	850.3	865.2	895.0	910.6	921.0
15°	653.2	680.7	703.0	729.8	755.1	778.9	798.2	825.0	851.1	863.0	880.1
17.5°	601.8	614.5	627.9	641.3	674.0	716.4	750.6	779.6	802.0	817.6	837.7
20°	548.3	560.9	575.8	588.5	608.5	639.0	681.4	731.3	758.1	774.4	793.8
22.5°	510.3	522.2	531.9	543.1	558.7	581.0	613.0	674.8	710.5	730.5	747.7
25°	469.4	484.3	494.7	502.9	515.5	540.1	566.1	601.1	665.1	680.7	704.5
27.5°	441.2	445.6	457.5	470.2	482.8	496.2	523.0	552.7	595.9	630.1	659.1
30°	407.7	418.8	430.0	435.2	446.4	465.7	482.1	514.1	547.5	574.3	609.3
32.5°	382.4	389.1	396.5	409.2	419.6	433.0	449.3	476.1	504.4	521.5	548.3
35°	354.1	358.6	374.2	379.4	389.8	403.2	419.6	440.4	470.9	484.3	503.6
37.5°	327.3	337.7	342.2	354.1	363.8	377.2	389.1	412.9	433.0	448.6	466.4
40°	306.5	311.0	319.1	329.6	337.7	348.2	363.0	380.2	401.7	414.4	430.0
42.5°	281.2	284.9	295.3	301.3	314.7	324.4	333.3	354.1	373.5	383.1	398.8
45°	253.7	262.6	269.3	281.2	288.6	300.6	311.7	326.6	344.4	355.6	364.5
47.5°	229.9	238.8	245.5	256.7	268.6	273.8	285.7	301.3	317.7	326.6	339.2
50°	210.5	213.5	226.2	231.4	244.0	254.4	262.6	276.0	293.9	299.1	309.5
52.5°	191.9	194.2	202.4	209.0	220.2	229.1	239.5	252.2	267.1	275.3	283.4
55°	175.6	177.1	180.8	188.2	195.7	206.8	216.5	228.4	241.0	250.0	257.4
57.5°	157.0	159.9	162.9	167.4	174.8	185.2	195.7	206.8	217.2	223.2	232.9
60°	135.4	139.9	145.1	150.3	155.5	162.9	174.8	185.2	194.9	200.1	207.6
62.5°	112.3	121.3	125.7	131.7	136.1	142.8	151.8	163.7	170.4	177.1	183.0
65°	101.2	101.9	102.7	108.6	116.8	123.5	131.7	140.6	151.0	155.5	159.9
67.5°	90.0	90.8	92.2	93.0	96.0	103.4	112.3	122.0	130.2	133.2	137.6
70°	78.9	78.9	81.8	82.6	83.3	84.1	91.5	101.2	108.6	112.3	117.5
72.5°	67.0	67.7	69.2	69.9	71.4	72.9	75.1	80.3	89.3	93.0	98.9
75°	55.1	55.8	56.5	57.3	59.5	60.3	62.5	65.5	69.2	73.6	77.4
77.5°	43.9	43.9	44.6	46.1	47.6	48.4	50.6	52.1	53.6	55.8	58.8
80°	32.7	33.5	33.5	35.0	35.0	35.7	36.5	38.7	40.2	41.7	43.1
82.5°	22.3	23.8	23.8	23.8	24.5	25.3	26.0	26.0	27.5	28.3	30.5
85°	13.4	14.1	14.1	14.1	13.4	14.9	14.9	15.6	15.6	15.6	16.4
87.5°	5.2	4.5	5.2	5.2	5.2	6.0	5.2	5.2	6.0	6.7	6.7
90°	11.8	11.9	12.1	12.2	12.4	10.7	8.9	7.2	5.5	4.6	4.1
92.5°	11.4	11.3	11.2	11.1	11.0	10.9	10.9	10.8	10.7	10.7	10.4
95°	22.8	22.8	22.8	22.8	22.8	22.6	22.4	22.3	22.1	22.0	21.6
97.5°	35.6	35.6	35.6	35.6	35.6	35.3	34.9	34.6	34.3	34.1	33.7
100°	49.1	49.1	49.1	49.1	49.1	48.9	48.6	48.4	48.1	48.0	47.7
102.5°	64.0	63.9	63.8	63.7	63.6	63.3	63.0	62.7	62.4	62.2	62.0
105°	78.8	78.7	78.5	78.4	78.2	78.0	77.9	77.7	77.6	77.5	77.4
107.5°	94.6	94.5	94.4	94.3	94.2	94.2	94.2	94.2	94.2	94.2	94.0
110°	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.4

TEST NUMBER: P1009985

CATALOG NUMBER: S122RDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	126.3	126.6	126.8	127.1	127.3	127.4	127.4	127.5	127.6	127.6	127.4
115°	143.3	143.4	143.5	143.5	143.6	143.8	143.9	144.1	144.2	144.3	144.1
117.5°	159.0	159.3	159.5	159.8	160.0	160.4	160.8	161.2	161.6	161.8	161.5
120°	175.6	175.6	175.6	175.6	175.6	176.2	176.9	177.5	178.2	178.5	178.2
122.5°	191.7	192.0	192.2	192.5	192.7	193.1	193.5	193.9	194.3	194.5	194.1
125°	208.1	208.3	208.6	208.8	209.0	209.2	209.5	209.7	210.0	210.1	209.7
127.5°	223.8	224.1	224.4	224.7	225.0	225.3	225.7	226.0	226.3	226.5	226.1
130°	240.4	240.5	240.7	240.8	241.0	241.2	241.3	241.5	241.6	241.7	241.2
132.5°	255.8	256.2	256.6	257.0	257.4	257.3	257.2	257.1	257.0	257.0	256.6
135°	272.0	272.1	272.2	272.2	272.3	272.1	272.0	271.8	271.7	271.6	271.2
137.5°	286.9	287.0	287.1	287.1	287.2	287.0	286.9	286.7	286.6	286.5	286.1
140°	302.2	302.2	302.2	302.2	302.2	301.8	301.4	301.0	300.6	300.4	300.0
142.5°	316.0	315.9	315.8	315.8	315.7	315.5	315.2	315.0	314.7	314.6	314.2
145°	329.9	329.8	329.7	329.7	329.6	329.1	328.6	328.1	327.6	327.4	327.1
147.5°	342.3	342.1	342.0	341.8	341.6	341.3	341.0	340.7	340.4	340.2	339.8
150°	354.0	353.7	353.5	353.2	353.0	352.7	352.4	352.1	351.8	351.6	351.4
152.5°	365.6	365.3	365.0	364.7	364.4	364.0	363.6	363.2	362.8	362.6	362.4
155°	375.2	374.8	374.4	374.0	373.6	373.4	373.2	372.9	372.7	372.6	372.5
157.5°	384.7	384.2	383.6	383.1	382.5	382.3	382.2	382.0	381.9	381.8	381.7
160°	392.6	392.1	391.6	391.2	390.7	390.6	390.5	390.4	390.3	390.3	390.2
162.5°	400.0	399.5	398.9	398.4	397.8	397.7	397.7	397.6	397.5	397.5	397.5
165°	406.0	405.5	405.0	404.4	403.9	403.9	403.9	403.9	403.9	403.9	403.9
167.5°	411.4	410.9	410.3	409.8	409.2	409.2	409.2	409.2	409.2	409.2	409.3
170°	415.6	415.1	414.6	414.0	413.5	413.6	413.6	413.7	413.8	413.8	413.9
172.5°	418.8	418.3	417.8	417.2	416.7	416.8	416.8	416.9	417.0	417.0	417.1
175°	421.0	420.5	419.9	419.4	418.8	419.0	419.1	419.3	419.4	419.5	419.6
177.5°	422.1	421.6	421.1	420.7	420.2	420.4	420.5	420.7	420.8	420.9	421.0
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3

TEST NUMBER: P1009985

CATALOG NUMBER: S122RDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1070.5	1070.5	1070.5	1070.5
2.5°	1051.2	1049.0	1062.3	1077.2
5°	1029.6	1033.3	1050.4	1071.3
7.5°	1007.3	1015.5	1035.6	1063.1
10°	976.0	990.9	1021.4	1049.7
12.5°	945.5	965.6	994.6	1028.1
15°	911.3	933.6	969.3	1009.5
17.5°	873.4	898.7	940.3	984.2
20°	833.2	866.7	910.6	958.2
22.5°	788.6	828.7	874.1	926.9
25°	745.4	789.3	834.7	895.7
27.5°	703.0	746.2	796.8	858.5
30°	660.6	700.0	754.4	820.6
32.5°	615.2	656.2	713.4	781.1
35°	573.6	614.5	668.1	735.0
37.5°	528.9	572.8	624.2	693.3
40°	476.9	528.2	578.0	644.2
42.5°	433.7	488.0	536.4	598.9
45°	399.5	450.8	491.0	552.0
47.5°	367.5	409.2	450.1	506.6
50°	337.0	369.0	411.4	462.0
52.5°	305.8	333.3	369.7	417.3
55°	277.5	303.5	336.3	372.7
57.5°	251.5	270.0	302.8	335.5
60°	222.4	241.8	267.1	294.6
62.5°	197.9	212.8	236.6	259.6
65°	171.8	186.0	203.8	225.4
67.5°	148.0	160.7	174.8	191.9
70°	126.5	136.1	146.6	161.4
72.5°	103.4	113.8	123.5	135.4
75°	84.8	89.3	97.5	105.6
77.5°	65.5	71.4	75.9	82.6
80°	46.9	52.1	53.6	58.8
82.5°	31.2	34.2	37.2	38.7
85°	17.9	19.3	22.3	23.1
87.5°	6.7	7.4	8.9	10.4
90°	3.2	2.3	1.3	0.4
92.5°	9.7	9.1	8.4	7.8
95°	20.8	20.1	19.3	18.5
97.5°	33.0	32.3	31.6	30.9
100°	47.0	46.4	45.7	45.1
102.5°	61.5	61.0	60.6	60.1
105°	77.1	76.9	76.6	76.4
107.5°	93.7	93.4	93.1	92.8
110°	109.9	109.4	108.9	108.4

TEST NUMBER: P1009985

CATALOG NUMBER: S122RDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	126.9	126.4	126.0	125.5
115°	143.6	143.1	142.7	142.2
117.5°	160.8	160.2	159.5	158.9
120°	177.5	176.9	176.2	175.6
122.5°	193.3	192.5	191.7	190.9
125°	209.0	208.3	207.6	206.9
127.5°	225.2	224.3	223.4	222.5
130°	240.2	239.1	238.1	237.1
132.5°	255.8	255.1	254.3	253.5
135°	270.3	269.4	268.6	267.7
137.5°	285.4	284.7	284.0	283.3
140°	299.3	298.6	297.9	297.2
142.5°	313.5	312.8	312.1	311.4
145°	326.6	326.0	325.5	324.9
147.5°	339.1	338.4	337.7	337.0
150°	350.9	350.4	350.0	349.5
152.5°	361.9	361.4	361.0	360.5
155°	372.2	372.0	371.7	371.5
157.5°	381.6	381.4	381.3	381.1
160°	390.1	389.9	389.8	389.6
162.5°	397.5	397.5	397.5	397.5
165°	404.0	404.1	404.1	404.2
167.5°	409.6	409.8	410.1	410.3
170°	414.2	414.4	414.7	414.9
172.5°	417.4	417.6	417.9	418.1
175°	419.9	420.1	420.4	420.6
177.5°	421.3	421.5	421.8	422.0
180°	421.3	421.3	421.3	421.3

(END OF REPORT)