

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010016

Luminaire Tested: S122RDIP-B485D530UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010016
REPORT IS A COMBINATION OF REPORTS P988316 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B485D530UB30-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3921.0 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010016

CATALOG NUMBER: S122RDIP-B485D530UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1010016

CATALOG NUMBER: S122RDIP-B485D530UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54
1	98	94	90	87	90	87	83	81	73	71	69	60	59	57	48	48	47
2	90	83	77	72	82	77	72	67	65	61	58	54	51	49	44	42	40
3	82	74	67	61	76	68	62	57	58	53	50	48	45	42	39	37	35
4	76	66	58	53	70	61	54	49	52	47	43	44	40	37	36	33	31
5	70	59	51	46	64	55	48	43	47	42	38	40	36	33	33	30	28
6	65	53	46	40	59	50	43	38	43	37	33	36	32	29	30	27	25
7	60	48	41	35	55	45	38	34	39	34	30	33	29	26	28	25	23
8	56	44	37	32	52	41	35	30	36	31	27	31	27	24	26	23	21
9	52	41	33	29	48	38	31	27	33	28	24	28	24	22	24	21	19
10	49	37	30	26	45	35	29	25	31	26	22	26	22	20	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16945	16945	16945	16945
5°	16986	17998	17044	14379
10°	16798	19025	16917	11875
15°	16433	19030	16712	8920
20°	15995	15731	16343	7359
25°	15464	9830	15797	6261
30°	14786	6293	15187	5389
35°	13959	4837	14411	4612
40°	13038	4066	13597	4034
45°	12056	3460	12560	3387
50°	11048	2940	11565	2930
55°	9931	2556	10467	2521
60°	8940	1948	9413	1924
65°	8013	1466	8489	1663
70°	6990	1171	7540	1355
75°	5907	898	6450	1026
80°	4694	610	5046	673
85°	3263	315	3574	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 15501 cd/sqm

TEST NUMBER: P1010016

CATALOG NUMBER: S122RDIP-B485D530UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.5	2.6
10°-20°	283.4	7.2
20°-30°	364.8	9.3
30°-40°	346.1	8.8
40°-50°	296.6	7.6
50°-60°	225.9	5.8
60°-70°	142.4	3.6
70°-80°	71.1	1.8
80°-90°	20.2	0.5
90°-100°	115.8	3.0
100°-110°	407.9	10.4
110°-120°	428.4	10.9
120°-130°	352.4	9.0
130°-140°	283.1	7.2
140°-150°	213.9	5.5
150°-160°	150.3	3.8
160°-170°	88.5	2.3
170°-180°	28.8	0.7
0°-30°	749.7	19.1
0°-40°	1095.8	27.9
0°-60°	1618.2	41.3
0°-90°	1851.9	47.2
90°-120°	952.1	24.3
90°-150°	1801.5	45.9
90°-180°	2069.0	52.8
0°-180°	3921.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1070	1070	1070	1070	1070	
5°	1071	1191	1075	952	1071	102
15°	1010	1344	1027	630	1010	284
25°	896	717	915	457	896	411
35°	735	353	759	337	735	460
45°	552	246	575	240	552	426
55°	373	170	393	168	373	336
65°	225	88	239	100	225	224
75°	106	47	115	54	106	114
85°	23	13	25	14	23	26
90°	1	19	1	19	1	3
95°	20	65	20	65	20	21
105°	70	644	70	644	70	74
115°	123	847	123	847	123	122
125°	171	687	171	687	171	152
135°	201	570	201	570	201	155
145°	230	455	230	455	230	144
155°	261	382	261	382	261	120
165°	284	335	284	335	284	80
175°	296	302	296	302	296	28
180°	297	297	297	297	297	

TEST NUMBER: P1010016

CATALOG NUMBER: S122RDIP-B485D530UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1077.2	1081.7	1083.9	1086.9	1093.6	1098.1	1104.7	1106.2	1105.5	1108.5	1100.3
5°	1071.3	1080.9	1089.9	1097.3	1109.2	1116.6	1124.8	1134.5	1136.7	1147.9	1141.2
7.5°	1063.1	1077.2	1089.9	1104.7	1122.6	1132.3	1144.9	1159.8	1166.5	1179.9	1183.6
10°	1049.7	1069.8	1091.4	1107.0	1131.5	1148.6	1160.5	1184.3	1200.0	1220.1	1217.1
12.5°	1028.1	1054.2	1083.2	1109.2	1141.2	1152.4	1174.7	1199.2	1219.3	1237.9	1254.3
15°	1009.5	1039.3	1071.3	1103.3	1139.7	1160.5	1182.9	1214.8	1236.4	1269.2	1283.3
17.5°	984.2	1022.2	1060.1	1095.8	1139.0	1162.8	1190.3	1221.5	1253.5	1284.8	1295.9
20°	958.2	999.1	1040.0	1088.4	1137.5	1160.5	1188.8	1227.5	1258.7	1283.3	1283.3
22.5°	926.9	976.8	1023.7	1069.8	1123.3	1156.8	1185.8	1231.2	1253.5	1258.7	1238.7
25°	895.7	945.5	996.9	1054.2	1115.2	1144.9	1177.7	1220.1	1227.5	1206.7	1154.6
27.5°	858.5	914.3	972.3	1034.1	1098.1	1135.2	1165.0	1193.3	1179.1	1123.3	1042.3
30°	820.6	880.8	946.3	1005.1	1082.4	1116.6	1141.9	1150.1	1105.5	1014.7	909.8
32.5°	781.1	839.9	909.1	979.8	1057.9	1090.6	1107.0	1085.4	1003.6	889.0	761.0
35°	735.0	801.2	873.4	947.0	1024.4	1049.0	1058.6	1005.8	900.9	752.9	625.7
37.5°	693.3	759.6	836.9	912.1	987.2	1000.6	990.9	908.3	775.2	628.6	504.4
40°	644.2	714.9	790.8	874.9	936.6	940.3	916.5	809.4	644.2	506.6	430.0
42.5°	598.9	670.3	746.2	831.7	878.6	865.9	834.0	693.3	537.9	436.7	374.9
45°	552.0	619.7	701.5	777.4	810.9	781.1	732.8	583.2	451.6	375.7	328.1
47.5°	506.6	569.9	650.9	723.9	729.8	696.3	639.0	488.8	391.3	330.3	291.6
50°	462.0	525.2	601.1	661.4	655.4	609.3	544.6	424.8	340.0	291.6	259.6
52.5°	417.3	474.6	548.3	595.9	570.6	526.0	462.0	360.1	296.8	254.4	229.9
55°	372.7	426.3	489.5	528.9	488.8	437.4	392.1	308.7	257.4	223.2	204.6
57.5°	335.5	377.9	435.9	459.8	411.4	371.2	331.8	265.6	223.2	198.6	177.1
60°	294.6	333.3	380.9	395.0	345.2	312.5	279.0	224.7	191.2	169.6	155.5
62.5°	259.6	291.6	328.1	328.1	284.2	259.6	234.3	188.2	160.7	143.6	136.9
65°	225.4	248.5	274.5	271.5	234.3	212.8	192.7	155.5	134.7	122.7	116.1
67.5°	191.9	209.8	226.9	216.5	189.7	171.1	152.5	125.7	111.6	103.4	94.5
70°	161.4	175.6	184.5	174.8	148.0	132.4	119.0	101.2	90.0	79.6	74.4
72.5°	135.4	141.3	144.3	132.4	110.1	101.2	91.5	78.9	69.2	64.0	62.5
75°	105.6	110.8	108.6	99.7	81.1	74.4	67.0	58.0	55.8	52.8	51.3
77.5°	82.6	82.6	78.9	70.7	58.0	52.8	49.8	45.4	43.1	42.4	40.9
80°	58.8	58.0	55.8	46.9	39.4	36.5	36.5	33.5	32.7	31.2	31.2
82.5°	38.7	38.7	35.7	28.3	26.0	25.3	24.5	23.1	23.1	22.3	22.3
85°	23.1	21.6	17.9	15.6	14.9	14.9	14.1	13.4	14.1	13.4	13.4
87.5°	10.4	8.2	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
90°	0.6	2.3	4.6	5.7	6.9	7.8	8.6	11.4	15.4	18.9	19.4
92.5°	8.6	12.0	16.6	19.4	24.0	27.2	30.3	45.7	67.4	86.8	88.0
95°	20.0	22.3	28.0	33.1	42.3	49.2	56.0	82.3	132.0	198.3	224.0
97.5°	29.7	33.1	39.4	46.9	57.1	64.8	72.6	106.3	175.4	282.3	365.1
100°	44.0	45.7	50.9	60.0	71.4	79.4	87.4	117.7	187.4	310.8	451.4
102.5°	57.1	58.3	63.4	72.6	84.6	92.6	100.6	128.0	188.0	300.0	454.2
105°	69.7	72.0	76.0	84.6	97.1	105.1	113.1	140.0	190.8	285.1	423.4
107.5°	83.4	85.1	89.1	97.1	109.7	117.7	125.7	152.0	197.1	277.1	394.8
110°	97.1	99.4	102.8	110.3	122.3	130.6	138.8	164.0	205.1	274.8	375.4

TEST NUMBER: P1010016

CATALOG NUMBER: S122RDIP-B485D530UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	109.7	112.0	116.0	122.8	134.3	142.9	151.4	175.4	213.7	275.4	362.8
115°	122.8	125.7	129.1	136.0	147.4	155.1	162.8	187.4	222.3	277.7	354.2
117.5°	136.6	138.8	142.3	148.6	159.4	167.4	175.4	198.3	231.4	281.1	349.7
120°	149.1	151.4	154.8	160.0	171.4	179.4	187.4	209.7	240.5	284.5	345.7
122.5°	161.1	162.8	166.3	172.0	183.4	191.7	200.0	220.5	248.5	288.5	343.4
125°	171.4	173.1	176.6	183.4	194.8	202.8	210.8	231.4	257.1	292.5	340.5
127.5°	180.0	182.3	186.8	194.3	205.1	213.4	221.7	241.7	265.1	296.5	338.8
130°	187.4	189.7	195.4	203.4	214.8	222.8	230.8	250.8	272.5	301.1	337.7
132.5°	194.3	197.1	203.4	212.0	224.0	232.0	240.0	258.8	280.0	305.7	337.1
135°	201.1	203.4	210.3	218.8	232.0	240.0	248.0	266.3	286.3	309.1	336.5
137.5°	207.4	210.3	217.1	226.3	239.4	246.8	254.3	272.5	291.4	312.5	336.5
140°	214.8	217.1	224.0	233.1	245.7	253.1	260.5	277.7	295.4	314.8	336.0
142.5°	222.3	224.0	230.3	239.4	251.4	258.2	265.1	281.7	298.8	316.5	336.0
145°	229.7	232.0	237.7	246.3	257.7	264.0	270.3	285.7	301.7	317.7	334.8
147.5°	237.7	239.4	245.1	253.1	262.8	268.6	274.3	289.1	303.4	318.3	333.1
150°	245.7	247.4	252.0	259.4	268.0	273.2	278.3	291.4	304.5	317.7	331.4
152.5°	253.7	254.3	258.8	265.1	273.1	277.7	282.3	293.7	305.1	316.5	328.5
155°	261.1	261.7	265.1	271.4	277.7	282.0	286.3	296.0	305.7	315.4	325.1
157.5°	267.4	268.0	270.8	276.5	281.7	285.4	289.1	297.7	305.7	313.1	321.7
160°	273.7	274.3	276.5	281.1	285.7	288.8	292.0	298.8	305.7	311.4	318.3
162.5°	280.0	279.4	281.7	285.1	289.1	291.4	293.7	299.4	305.1	309.7	315.4
165°	284.5	284.0	285.1	288.5	291.4	293.1	294.8	300.0	304.0	307.4	311.4
167.5°	288.5	288.0	289.1	291.4	293.7	294.8	296.0	300.0	303.4	305.1	308.0
170°	292.5	291.4	292.0	293.7	294.8	295.6	296.5	299.4	302.3	303.4	305.1
172.5°	294.8	294.3	293.7	295.4	296.0	296.6	297.1	298.8	300.5	301.1	301.7
175°	296.5	296.0	295.4	296.5	296.5	296.8	297.1	298.3	299.4	298.8	299.4
177.5°	297.7	296.5	296.0	297.1	297.1	297.1	297.1	297.7	298.8	297.7	297.1
180°	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1

TEST NUMBER: P1010016

CATALOG NUMBER: S122RDIP-B485D530UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1108.5	1110.0	1112.2	1122.6	1124.1	1127.1	1125.6	1125.6	1126.3	1124.8	1125.6
5°	1156.1	1158.3	1169.5	1182.1	1185.1	1182.1	1185.8	1191.0	1191.0	1191.0	1189.6
7.5°	1200.7	1208.9	1221.5	1240.1	1243.9	1247.6	1254.3	1249.8	1251.3	1258.0	1255.8
10°	1243.9	1255.8	1269.9	1285.5	1293.7	1298.9	1301.9	1308.6	1324.2	1306.4	1313.0
12.5°	1284.8	1301.9	1316.8	1333.9	1339.8	1346.5	1348.8	1354.7	1354.7	1354.0	1359.2
15°	1311.6	1327.2	1340.6	1351.7	1353.2	1351.7	1350.2	1351.0	1353.2	1344.3	1349.5
17.5°	1317.5	1319.0	1323.5	1319.0	1319.7	1304.1	1295.2	1293.0	1272.1	1272.9	1290.0
20°	1288.5	1263.2	1256.5	1232.0	1217.1	1176.9	1175.4	1164.3	1120.4	1133.8	1130.8
22.5°	1208.9	1165.7	1108.5	1080.2	1066.1	1023.7	990.9	967.9	952.2	936.6	929.9
25°	1104.0	1034.1	953.0	897.2	889.0	849.6	789.3	761.0	727.6	717.2	735.0
27.5°	968.6	877.8	786.3	700.8	685.2	649.5	619.0	598.9	560.2	558.0	559.4
30°	784.9	693.3	616.7	560.9	522.2	505.9	485.8	470.9	455.3	461.2	462.7
32.5°	645.0	558.0	486.5	456.8	438.9	428.5	411.4	401.7	395.0	392.8	392.1
35°	512.6	454.5	422.6	393.5	383.1	375.7	363.0	358.6	352.6	353.4	353.4
37.5°	438.9	390.6	366.8	351.9	342.2	338.5	330.3	325.8	322.1	320.6	322.9
40°	378.7	345.2	330.3	316.9	308.7	307.2	302.8	297.6	293.1	293.9	296.1
42.5°	334.8	315.4	297.6	287.2	281.2	279.0	275.3	271.5	271.5	269.3	268.6
45°	299.8	284.2	269.3	259.6	255.9	252.9	248.5	247.7	244.8	245.5	246.2
47.5°	268.6	255.9	244.8	235.1	231.4	230.6	226.2	223.2	223.2	222.4	221.7
50°	240.3	227.6	218.0	212.8	207.6	206.1	205.3	204.6	203.1	203.1	203.8
52.5°	217.2	204.6	197.1	192.7	189.7	188.2	188.2	187.5	187.5	187.5	186.7
55°	191.9	181.5	175.6	174.1	172.6	171.8	171.1	169.6	168.9	170.4	168.9
57.5°	168.1	164.4	159.2	157.7	154.0	154.0	151.8	150.3	148.8	150.3	150.3
60°	149.5	144.3	141.3	136.9	133.9	130.9	127.2	126.5	125.0	124.2	123.5
62.5°	130.2	125.7	118.3	111.6	107.1	104.2	102.7	101.9	101.9	101.2	101.2
65°	108.6	98.2	94.5	92.2	91.5	90.8	89.3	88.5	89.3	88.5	89.3
67.5°	84.8	83.3	81.1	79.6	78.9	78.1	78.1	77.4	77.4	77.4	77.4
70°	73.6	69.9	69.2	67.7	67.7	67.0	67.0	67.0	67.0	66.2	67.7
72.5°	61.0	58.8	58.0	57.3	57.3	57.3	56.5	56.5	56.5	55.8	56.5
75°	49.8	49.1	47.6	47.6	46.9	47.6	46.9	46.9	46.1	46.9	46.9
77.5°	40.2	39.4	38.7	38.7	37.9	37.9	37.9	37.9	37.9	37.9	38.7
80°	30.5	29.8	29.0	29.8	29.0	29.8	29.0	29.0	29.8	29.0	29.0
82.5°	22.3	21.6	21.6	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8
85°	13.4	12.6	12.6	13.4	12.6	13.4	12.6	12.6	12.6	13.4	13.4
87.5°	6.0	6.7	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.7
90°	18.9	18.3	17.1	18.3	18.6	18.9	18.9	18.9	18.9	18.9	18.9
92.5°	73.7	57.7	49.1	42.9	40.6	38.3	37.7	35.4	36.0	34.9	36.0
95°	196.0	149.7	114.8	90.8	84.6	78.3	70.8	66.3	64.6	65.1	64.6
97.5°	368.0	306.3	244.5	186.8	169.7	152.6	130.3	118.8	112.6	109.1	112.6
100°	533.7	521.7	450.8	372.5	338.0	303.4	256.0	231.4	214.8	204.5	214.8
102.5°	595.4	662.8	660.5	608.5	571.4	534.2	481.7	435.4	413.7	398.8	413.7
105°	575.4	694.2	758.8	766.2	756.8	747.3	711.9	676.5	651.9	643.9	651.9
107.5°	533.1	660.5	756.5	812.5	823.9	835.3	834.8	829.6	822.2	809.1	822.2
110°	493.7	614.2	716.5	789.6	813.0	836.5	861.1	871.9	877.0	876.5	877.0

TEST NUMBER: P1010016

CATALOG NUMBER: S122RDIP-B485D530UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	466.2	571.9	669.1	748.5	776.2	803.9	840.5	860.5	871.3	875.3	871.3
115°	444.5	538.8	626.8	701.6	731.0	760.5	801.1	827.3	842.2	847.3	842.2
117.5°	429.7	511.4	590.2	659.9	687.9	715.9	757.6	785.6	801.1	805.1	801.1
120°	418.2	491.9	562.8	623.4	649.4	675.4	715.4	742.2	758.8	764.5	758.8
122.5°	408.5	476.5	539.9	596.5	619.4	642.2	677.1	703.4	717.6	722.2	717.6
125°	399.4	461.7	520.5	570.8	592.2	613.6	646.8	668.5	682.8	687.4	682.8
127.5°	390.8	446.8	501.1	549.1	569.1	589.1	618.2	638.8	651.4	654.8	651.4
130°	382.2	432.5	481.7	526.8	545.6	564.5	592.5	611.9	623.4	627.9	623.4
132.5°	375.4	418.8	463.4	503.9	521.3	538.8	566.2	585.7	595.9	599.9	595.9
135°	369.1	406.2	444.0	481.7	497.7	513.7	538.2	557.1	567.4	569.7	567.4
137.5°	364.5	396.0	428.5	459.4	473.6	487.9	511.4	527.9	537.1	540.5	537.1
140°	360.5	386.2	413.7	440.0	452.6	465.1	483.4	498.2	506.8	510.2	506.8
142.5°	356.5	378.2	400.5	422.2	432.2	442.2	459.4	472.5	479.9	479.9	479.9
145°	353.1	370.8	389.7	407.4	415.7	424.0	437.7	447.4	453.1	454.8	453.1
147.5°	349.7	365.1	380.5	394.8	401.1	407.4	419.4	427.4	431.4	432.5	431.4
150°	345.1	358.8	371.4	383.4	388.5	393.7	402.2	409.1	412.5	413.1	412.5
152.5°	341.1	352.5	364.0	373.7	378.0	382.2	388.5	394.2	396.5	396.5	396.5
155°	336.0	346.8	356.0	364.5	367.6	370.8	377.1	381.1	383.4	382.2	383.4
157.5°	331.4	340.0	348.0	355.4	358.0	360.5	365.1	368.5	369.7	369.7	369.7
160°	326.3	333.7	340.0	346.2	348.2	350.2	354.2	357.1	357.7	357.7	357.7
162.5°	321.7	327.4	332.5	337.7	339.1	340.5	344.5	346.2	346.8	346.2	346.8
165°	316.5	321.1	325.1	329.1	330.2	331.4	333.7	336.0	336.0	335.4	336.0
167.5°	311.4	314.8	318.3	321.1	322.2	323.4	324.5	325.7	325.7	325.1	325.7
170°	307.4	310.3	312.0	314.3	314.8	315.4	316.0	317.7	317.1	316.0	317.1
172.5°	303.4	305.1	306.3	308.0	308.2	308.5	309.1	309.7	309.1	308.5	309.1
175°	300.0	301.7	302.3	302.8	303.1	303.4	303.4	304.0	303.4	302.3	303.4
177.5°	297.7	298.8	298.8	299.4	299.4	299.4	299.4	299.4	298.8	297.7	298.8
180°	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1

TEST NUMBER: P1010016

CATALOG NUMBER: S122RDIP-B485D530UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1128.6	1123.3	1121.9	1123.3	1121.9	1122.6	1117.4	1098.1	1103.3	1095.1	1099.5
5°	1192.5	1188.1	1178.4	1176.9	1175.4	1173.9	1166.5	1149.4	1142.7	1131.5	1130.8
7.5°	1253.5	1253.5	1246.1	1240.9	1234.2	1229.0	1219.3	1194.0	1183.6	1170.2	1162.8
10°	1313.8	1294.4	1302.6	1297.4	1281.1	1278.1	1260.2	1245.4	1225.3	1211.9	1200.0
12.5°	1356.9	1351.0	1343.5	1339.1	1334.6	1325.0	1313.0	1275.1	1264.7	1237.9	1224.5
15°	1355.5	1351.7	1354.0	1354.0	1352.5	1350.2	1340.6	1313.0	1295.2	1269.2	1246.1
17.5°	1282.5	1292.2	1301.9	1308.6	1323.5	1330.2	1339.1	1322.7	1311.6	1289.2	1264.7
20°	1155.3	1179.1	1207.4	1213.4	1226.8	1266.2	1284.0	1298.2	1302.6	1295.2	1275.1
22.5°	978.3	998.4	1066.8	1065.3	1084.7	1131.5	1183.6	1226.0	1259.5	1278.1	1270.6
25°	766.3	794.5	831.0	858.5	921.7	991.7	1056.4	1124.1	1182.1	1233.4	1246.1
27.5°	579.5	616.7	645.7	682.2	714.2	796.8	880.1	985.7	1053.4	1150.9	1201.5
30°	468.7	485.8	514.8	531.9	547.5	610.8	705.3	809.4	928.4	1040.8	1127.8
32.5°	400.2	412.1	433.7	441.2	457.5	499.9	559.4	654.7	777.4	913.6	1028.1
35°	359.3	372.0	376.4	383.1	396.5	423.3	464.2	533.4	644.2	777.4	914.3
37.5°	324.4	331.1	343.7	348.2	352.6	372.7	400.2	448.6	522.2	631.6	783.4
40°	299.8	303.5	310.2	313.9	316.9	331.1	355.6	388.3	442.6	526.0	665.8
42.5°	273.8	278.2	282.7	287.2	290.9	302.0	316.9	348.2	384.6	447.8	549.0
45°	248.5	251.5	256.7	259.6	264.8	273.8	287.2	308.7	341.5	381.6	463.5
47.5°	225.4	229.1	231.4	235.1	238.8	248.5	261.1	275.3	302.0	341.5	401.0
50°	204.6	209.0	212.0	212.8	215.7	224.7	235.1	250.7	267.8	298.3	350.4
52.5°	189.7	190.4	192.7	195.7	194.9	200.1	209.8	221.7	239.5	264.1	302.0
55°	172.6	174.8	176.3	177.1	177.1	181.5	186.7	197.9	212.0	232.1	264.1
57.5°	151.0	153.3	157.7	159.2	161.4	163.7	165.9	173.3	185.2	204.6	230.6
60°	128.7	130.2	134.7	137.6	139.1	145.1	148.0	154.0	160.7	174.8	199.4
62.5°	103.4	104.9	107.1	110.1	113.1	122.0	129.4	135.4	140.6	150.3	170.4
65°	90.0	90.8	92.2	93.0	93.7	97.5	104.2	112.3	122.0	129.4	141.3
67.5°	78.1	78.9	79.6	81.1	81.8	82.6	85.6	87.8	97.5	107.9	116.8
70°	67.0	68.4	69.2	69.2	69.9	71.4	72.9	75.9	78.9	84.1	95.2
72.5°	56.5	57.3	58.8	58.8	58.8	60.3	61.7	63.2	64.7	67.7	72.2
75°	46.9	48.4	48.4	48.4	49.1	49.1	50.6	52.1	53.6	55.8	57.3
77.5°	38.7	38.7	38.7	38.7	39.4	39.4	40.2	41.7	42.4	43.1	44.6
80°	29.0	29.8	29.8	29.8	30.5	30.5	30.5	32.0	32.7	32.7	34.2
82.5°	21.6	21.6	21.6	22.3	21.6	22.3	22.3	23.1	22.3	23.1	23.8
85°	13.4	13.4	13.4	14.1	14.1	14.1	14.1	14.1	14.1	14.1	14.9
87.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	7.4	6.7	6.7
90°	18.9	18.9	18.9	18.6	18.3	17.1	18.3	18.9	19.4	18.9	15.4
92.5°	35.4	37.7	38.3	40.6	42.9	49.1	57.7	73.7	88.0	86.8	67.4
95°	66.3	70.8	78.3	84.6	90.8	114.8	149.7	196.0	224.0	198.3	132.0
97.5°	118.8	130.3	152.6	169.7	186.8	244.5	306.3	368.0	365.1	282.3	175.4
100°	231.4	256.0	303.4	338.0	372.5	450.8	521.7	533.7	451.4	310.8	187.4
102.5°	435.4	481.7	534.2	571.4	608.5	660.5	662.8	595.4	454.2	300.0	188.0
105°	676.5	711.9	747.3	756.8	766.2	758.8	694.2	575.4	423.4	285.1	190.8
107.5°	829.6	834.8	835.3	823.9	812.5	756.5	660.5	533.1	394.8	277.1	197.1
110°	871.9	861.1	836.5	813.0	789.6	716.5	614.2	493.7	375.4	274.8	205.1

TEST NUMBER: P1010016

CATALOG NUMBER: S122RDIP-B485D530UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	860.5	840.5	803.9	776.2	748.5	669.1	571.9	466.2	362.8	275.4	213.7
115°	827.3	801.1	760.5	731.0	701.6	626.8	538.8	444.5	354.2	277.7	222.3
117.5°	785.6	757.6	715.9	687.9	659.9	590.2	511.4	429.7	349.7	281.1	231.4
120°	742.2	715.4	675.4	649.4	623.4	562.8	491.9	418.2	345.7	284.5	240.5
122.5°	703.4	677.1	642.2	619.4	596.5	539.9	476.5	408.5	343.4	288.5	248.5
125°	668.5	646.8	613.6	592.2	570.8	520.5	461.7	399.4	340.5	292.5	257.1
127.5°	638.8	618.2	589.1	569.1	549.1	501.1	446.8	390.8	338.8	296.5	265.1
130°	611.9	592.5	564.5	545.6	526.8	481.7	432.5	382.2	337.7	301.1	272.5
132.5°	585.7	566.2	538.8	521.3	503.9	463.4	418.8	375.4	337.1	305.7	280.0
135°	557.1	538.2	513.7	497.7	481.7	444.0	406.2	369.1	336.5	309.1	286.3
137.5°	527.9	511.4	487.9	473.6	459.4	428.5	396.0	364.5	336.5	312.5	291.4
140°	498.2	483.4	465.1	452.6	440.0	413.7	386.2	360.5	336.0	314.8	295.4
142.5°	472.5	459.4	442.2	432.2	422.2	400.5	378.2	356.5	336.0	316.5	298.8
145°	447.4	437.7	424.0	415.7	407.4	389.7	370.8	353.1	334.8	317.7	301.7
147.5°	427.4	419.4	407.4	401.1	394.8	380.5	365.1	349.7	333.1	318.3	303.4
150°	409.1	402.2	393.7	388.5	383.4	371.4	358.8	345.1	331.4	317.7	304.5
152.5°	394.2	388.5	382.2	378.0	373.7	364.0	352.5	341.1	328.5	316.5	305.1
155°	381.1	377.1	370.8	367.6	364.5	356.0	346.8	336.0	325.1	315.4	305.7
157.5°	368.5	365.1	360.5	358.0	355.4	348.0	340.0	331.4	321.7	313.1	305.7
160°	357.1	354.2	350.2	348.2	346.2	340.0	333.7	326.3	318.3	311.4	305.7
162.5°	346.2	344.5	340.5	339.1	337.7	332.5	327.4	321.7	315.4	309.7	305.1
165°	336.0	333.7	331.4	330.2	329.1	325.1	321.1	316.5	311.4	307.4	304.0
167.5°	325.7	324.5	323.4	322.2	321.1	318.3	314.8	311.4	308.0	305.1	303.4
170°	317.7	316.0	315.4	314.8	314.3	312.0	310.3	307.4	305.1	303.4	302.3
172.5°	309.7	309.1	308.5	308.2	308.0	306.3	305.1	303.4	301.7	301.1	300.5
175°	304.0	303.4	303.4	303.1	302.8	302.3	301.7	300.0	299.4	298.8	299.4
177.5°	299.4	299.4	299.4	299.4	299.4	298.8	298.8	297.7	297.1	297.7	298.8
180°	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1

TEST NUMBER: P1010016

CATALOG NUMBER: S122RDIP-B485D530UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1092.8	1089.1	1089.1	1086.9	1086.9	1075.0	1075.0	1078.7	1074.2	1069.0	1061.6
5°	1121.1	1112.9	1110.7	1107.7	1098.1	1083.2	1077.2	1075.0	1066.1	1054.9	1042.3
7.5°	1147.9	1134.5	1127.8	1121.1	1108.5	1087.6	1075.7	1067.5	1054.2	1037.0	1020.7
10°	1173.9	1156.8	1139.7	1131.5	1113.7	1087.6	1070.5	1057.1	1037.8	1014.7	991.7
12.5°	1197.7	1162.0	1159.1	1142.7	1116.6	1086.9	1060.9	1041.5	1017.0	990.2	963.4
15°	1218.6	1182.1	1164.3	1149.4	1115.2	1078.0	1050.4	1026.6	993.9	963.4	930.7
17.5°	1229.0	1189.6	1177.7	1153.1	1118.1	1069.8	1032.6	1003.6	967.9	931.4	894.2
20°	1239.4	1193.3	1173.9	1156.8	1109.2	1054.2	1012.5	979.0	939.6	896.4	855.5
22.5°	1244.6	1193.3	1170.2	1146.4	1100.3	1037.0	987.9	948.5	902.4	858.5	809.4
25°	1235.7	1188.8	1161.3	1136.7	1084.7	1016.2	959.7	915.0	865.9	816.1	766.3
27.5°	1213.4	1178.4	1146.4	1121.1	1063.1	989.4	929.9	879.3	828.7	773.0	722.4
30°	1171.7	1156.1	1130.8	1102.5	1039.3	965.6	895.0	842.9	787.1	731.3	678.5
32.5°	1107.0	1120.4	1104.0	1079.5	1011.0	932.9	857.8	804.9	743.9	683.7	635.3
35°	1028.1	1075.7	1066.8	1049.7	981.3	897.9	822.8	758.8	697.8	636.8	588.5
37.5°	941.8	1014.0	1021.4	1011.0	947.0	862.2	779.6	717.2	654.7	592.9	543.8
40°	823.5	934.4	958.2	962.7	911.3	819.1	732.8	671.8	610.0	549.8	490.3
42.5°	714.9	854.8	884.5	903.1	865.9	776.7	689.6	621.9	560.9	506.6	447.1
45°	613.0	758.8	807.2	831.0	814.6	728.3	638.3	575.1	519.3	469.4	412.1
47.5°	508.1	654.7	722.4	760.3	760.3	679.2	589.2	526.7	473.1	430.7	380.2
50°	438.2	560.2	630.1	680.0	693.3	629.4	544.6	483.6	433.0	386.8	348.2
52.5°	373.5	482.8	540.8	592.9	631.6	575.8	494.7	439.7	389.8	346.7	316.2
55°	322.9	404.7	457.5	514.8	558.0	521.5	446.4	392.8	349.7	313.9	287.9
57.5°	274.5	345.9	389.1	439.7	485.8	458.3	398.0	351.9	313.9	282.7	259.6
60°	233.6	291.6	325.1	364.5	421.8	402.5	352.6	310.2	279.7	251.5	232.1
62.5°	198.6	244.8	273.0	301.3	353.4	344.4	305.8	273.0	247.0	223.2	206.8
65°	162.9	200.9	223.2	247.7	289.4	293.1	261.9	238.8	215.0	194.2	179.3
67.5°	131.7	161.4	181.5	202.4	235.8	246.2	224.7	205.3	185.2	168.1	154.7
70°	106.4	127.2	142.1	158.5	186.0	198.6	187.5	174.1	157.7	143.6	131.7
72.5°	84.1	97.5	106.4	119.0	141.3	154.0	153.3	141.3	129.4	119.8	110.1
75°	61.7	72.2	79.6	87.8	105.6	117.5	120.5	115.3	103.4	96.0	88.5
77.5°	46.9	52.8	56.5	62.5	75.1	85.6	90.0	88.5	80.3	74.4	69.2
80°	35.7	37.2	38.7	40.9	51.3	61.0	64.0	63.2	58.8	56.5	50.6
82.5°	25.3	26.0	26.8	27.5	31.2	39.4	42.4	43.9	40.2	37.9	32.7
85°	14.9	15.6	15.6	17.1	17.9	20.1	25.3	25.3	24.5	21.6	20.8
87.5°	7.4	7.4	6.7	6.7	7.4	8.2	9.7	11.2	9.7	8.9	8.2
90°	11.4	8.6	7.8	6.9	5.7	4.6	2.3	0.6	2.3	4.6	5.7
92.5°	45.7	30.3	27.2	24.0	19.4	16.6	12.0	8.6	12.0	16.6	19.4
95°	82.3	56.0	49.2	42.3	33.1	28.0	22.3	20.0	22.3	28.0	33.1
97.5°	106.3	72.6	64.8	57.1	46.9	39.4	33.1	29.7	33.1	39.4	46.9
100°	117.7	87.4	79.4	71.4	60.0	50.9	45.7	44.0	45.7	50.9	60.0
102.5°	128.0	100.6	92.6	84.6	72.6	63.4	58.3	57.1	58.3	63.4	72.6
105°	140.0	113.1	105.1	97.1	84.6	76.0	72.0	69.7	72.0	76.0	84.6
107.5°	152.0	125.7	117.7	109.7	97.1	89.1	85.1	83.4	85.1	89.1	97.1
110°	164.0	138.8	130.6	122.3	110.3	102.8	99.4	97.1	99.4	102.8	110.3

TEST NUMBER: P1010016

CATALOG NUMBER: S122RDIP-B485D530UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	175.4	151.4	142.9	134.3	122.8	116.0	112.0	109.7	112.0	116.0	122.8
115°	187.4	162.8	155.1	147.4	136.0	129.1	125.7	122.8	125.7	129.1	136.0
117.5°	198.3	175.4	167.4	159.4	148.6	142.3	138.8	136.6	138.8	142.3	148.6
120°	209.7	187.4	179.4	171.4	160.0	154.8	151.4	149.1	151.4	154.8	160.0
122.5°	220.5	200.0	191.7	183.4	172.0	166.3	162.8	161.1	162.8	166.3	172.0
125°	231.4	210.8	202.8	194.8	183.4	176.6	173.1	171.4	173.1	176.6	183.4
127.5°	241.7	221.7	213.4	205.1	194.3	186.8	182.3	180.0	182.3	186.8	194.3
130°	250.8	230.8	222.8	214.8	203.4	195.4	189.7	187.4	189.7	195.4	203.4
132.5°	258.8	240.0	232.0	224.0	212.0	203.4	197.1	194.3	197.1	203.4	212.0
135°	266.3	248.0	240.0	232.0	218.8	210.3	203.4	201.1	203.4	210.3	218.8
137.5°	272.5	254.3	246.8	239.4	226.3	217.1	210.3	207.4	210.3	217.1	226.3
140°	277.7	260.5	253.1	245.7	233.1	224.0	217.1	214.8	217.1	224.0	233.1
142.5°	281.7	265.1	258.2	251.4	239.4	230.3	224.0	222.3	224.0	230.3	239.4
145°	285.7	270.3	264.0	257.7	246.3	237.7	232.0	229.7	232.0	237.7	246.3
147.5°	289.1	274.3	268.6	262.8	253.1	245.1	239.4	237.7	239.4	245.1	253.1
150°	291.4	278.3	273.2	268.0	259.4	252.0	247.4	245.7	247.4	252.0	259.4
152.5°	293.7	282.3	277.7	273.1	265.1	258.8	254.3	253.7	254.3	258.8	265.1
155°	296.0	286.3	282.0	277.7	271.4	265.1	261.7	261.1	261.7	265.1	271.4
157.5°	297.7	289.1	285.4	281.7	276.5	270.8	268.0	267.4	268.0	270.8	276.5
160°	298.8	292.0	288.8	285.7	281.1	276.5	274.3	273.7	274.3	276.5	281.1
162.5°	299.4	293.7	291.4	289.1	285.1	281.7	279.4	280.0	279.4	281.7	285.1
165°	300.0	294.8	293.1	291.4	288.5	285.1	284.0	284.5	284.0	285.1	288.5
167.5°	300.0	296.0	294.8	293.7	291.4	289.1	288.0	288.5	288.0	289.1	291.4
170°	299.4	296.5	295.6	294.8	293.7	292.0	291.4	292.5	291.4	292.0	293.7
172.5°	298.8	297.1	296.6	296.0	295.4	293.7	294.3	294.8	294.3	293.7	295.4
175°	298.3	297.1	296.8	296.5	296.5	295.4	296.0	296.5	296.0	295.4	296.5
177.5°	297.7	297.1	297.1	297.1	297.1	296.0	296.5	297.7	296.5	296.0	297.1
180°	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1

TEST NUMBER: P1010016

CATALOG NUMBER: S122RDIP-B485D530UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1058.6	1059.4	1061.6	1054.9	1044.5	1040.0	1026.6	1024.4	1022.2	1022.2	1024.4
5°	1034.8	1031.8	1032.6	1019.9	1005.1	996.1	977.5	980.5	970.8	964.9	966.4
7.5°	1008.8	1000.6	999.9	983.5	964.9	948.5	929.2	924.7	915.8	905.4	900.9
10°	976.0	970.1	958.9	940.3	916.5	903.1	877.1	861.5	859.2	843.6	837.7
12.5°	942.6	932.2	921.0	895.0	868.2	846.6	827.3	810.1	798.2	784.9	775.9
15°	903.9	891.2	878.6	851.1	819.8	798.2	769.2	743.9	709.0	681.4	665.8
17.5°	861.5	847.3	830.2	799.7	769.2	739.5	685.9	656.2	631.6	615.2	605.6
20°	817.6	802.0	784.9	754.4	701.5	649.5	619.7	596.6	581.8	565.4	553.5
22.5°	771.5	755.1	736.5	688.9	633.1	596.6	573.6	552.0	530.4	521.5	515.5
25°	728.3	713.4	689.6	624.9	581.0	547.5	521.5	507.4	496.2	484.3	473.1
27.5°	683.7	656.2	622.7	568.4	540.8	506.6	488.0	477.6	458.3	450.1	444.9
30°	630.1	599.6	567.6	528.9	496.9	473.1	456.0	438.9	427.8	419.6	410.7
32.5°	575.8	546.8	526.7	486.5	462.7	438.2	421.8	411.4	395.0	389.8	386.1
35°	528.9	504.4	486.5	453.8	431.5	409.2	397.3	381.6	371.2	361.6	355.6
37.5°	482.8	469.4	450.8	423.3	399.5	381.6	365.3	360.1	345.9	340.7	334.8
40°	450.8	430.7	415.1	391.3	371.2	351.9	341.5	329.6	319.9	311.7	309.5
42.5°	412.1	397.3	388.3	362.3	341.5	330.3	317.7	304.3	296.8	290.1	282.0
45°	383.1	369.7	357.1	336.3	317.7	303.5	292.4	283.4	270.8	267.8	255.2
47.5°	352.6	339.2	329.6	308.7	291.6	278.2	270.0	258.1	247.7	241.0	235.1
50°	322.1	311.0	302.0	284.2	269.3	255.2	244.0	232.1	227.6	216.5	212.8
52.5°	293.1	285.7	276.0	258.9	244.0	232.1	220.2	210.5	203.8	197.9	193.4
55°	268.6	256.7	252.2	233.6	220.9	208.3	197.9	191.9	183.8	180.0	176.3
57.5°	241.0	234.3	226.9	212.8	198.6	186.7	179.3	170.4	165.9	161.4	158.5
60°	217.2	207.6	201.6	189.7	177.1	165.9	159.2	152.5	146.6	142.8	136.9
62.5°	189.7	182.3	178.5	165.9	155.5	145.1	139.1	132.4	128.0	121.3	113.8
65°	165.9	159.9	155.5	145.1	135.4	125.7	119.8	111.6	105.6	101.9	101.2
67.5°	145.1	140.6	133.9	124.2	114.6	107.1	100.4	93.7	93.0	91.5	91.5
70°	122.0	117.5	113.8	103.4	95.2	87.0	85.6	83.3	81.1	80.3	78.9
72.5°	101.9	98.2	93.7	84.8	76.6	74.4	72.9	71.4	69.2	68.4	67.7
75°	82.6	77.4	74.4	66.2	64.0	62.5	61.0	58.8	57.3	56.5	55.1
77.5°	63.2	58.0	58.0	53.6	52.1	49.8	48.4	46.9	46.1	44.6	44.6
80°	44.6	44.6	43.1	40.9	38.7	37.9	35.7	35.0	34.2	35.0	33.5
82.5°	32.7	29.8	29.8	28.3	26.8	26.0	24.5	24.5	23.8	23.8	23.8
85°	18.6	18.6	17.9	16.4	15.6	15.6	14.9	14.9	14.1	14.1	13.4
87.5°	7.4	6.7	7.4	6.7	6.7	6.0	6.0	6.0	5.2	6.0	5.2
90°	6.9	7.8	8.6	11.4	15.4	18.9	19.4	18.9	18.3	17.1	18.3
92.5°	24.0	27.2	30.3	45.7	67.4	86.8	88.0	73.7	57.7	49.1	42.9
95°	42.3	49.2	56.0	82.3	132.0	198.3	224.0	196.0	149.7	114.8	90.8
97.5°	57.1	64.8	72.6	106.3	175.4	282.3	365.1	368.0	306.3	244.5	186.8
100°	71.4	79.4	87.4	117.7	187.4	310.8	451.4	533.7	521.7	450.8	372.5
102.5°	84.6	92.6	100.6	128.0	188.0	300.0	454.2	595.4	662.8	660.5	608.5
105°	97.1	105.1	113.1	140.0	190.8	285.1	423.4	575.4	694.2	758.8	766.2
107.5°	109.7	117.7	125.7	152.0	197.1	277.1	394.8	533.1	660.5	756.5	812.5
110°	122.3	130.6	138.8	164.0	205.1	274.8	375.4	493.7	614.2	716.5	789.6

TEST NUMBER: P1010016

CATALOG NUMBER: S122RDIP-B485D530UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	134.3	142.9	151.4	175.4	213.7	275.4	362.8	466.2	571.9	669.1	748.5
115°	147.4	155.1	162.8	187.4	222.3	277.7	354.2	444.5	538.8	626.8	701.6
117.5°	159.4	167.4	175.4	198.3	231.4	281.1	349.7	429.7	511.4	590.2	659.9
120°	171.4	179.4	187.4	209.7	240.5	284.5	345.7	418.2	491.9	562.8	623.4
122.5°	183.4	191.7	200.0	220.5	248.5	288.5	343.4	408.5	476.5	539.9	596.5
125°	194.8	202.8	210.8	231.4	257.1	292.5	340.5	399.4	461.7	520.5	570.8
127.5°	205.1	213.4	221.7	241.7	265.1	296.5	338.8	390.8	446.8	501.1	549.1
130°	214.8	222.8	230.8	250.8	272.5	301.1	337.7	382.2	432.5	481.7	526.8
132.5°	224.0	232.0	240.0	258.8	280.0	305.7	337.1	375.4	418.8	463.4	503.9
135°	232.0	240.0	248.0	266.3	286.3	309.1	336.5	369.1	406.2	444.0	481.7
137.5°	239.4	246.8	254.3	272.5	291.4	312.5	336.5	364.5	396.0	428.5	459.4
140°	245.7	253.1	260.5	277.7	295.4	314.8	336.0	360.5	386.2	413.7	440.0
142.5°	251.4	258.2	265.1	281.7	298.8	316.5	336.0	356.5	378.2	400.5	422.2
145°	257.7	264.0	270.3	285.7	301.7	317.7	334.8	353.1	370.8	389.7	407.4
147.5°	262.8	268.6	274.3	289.1	303.4	318.3	333.1	349.7	365.1	380.5	394.8
150°	268.0	273.2	278.3	291.4	304.5	317.7	331.4	345.1	358.8	371.4	383.4
152.5°	273.1	277.7	282.3	293.7	305.1	316.5	328.5	341.1	352.5	364.0	373.7
155°	277.7	282.0	286.3	296.0	305.7	315.4	325.1	336.0	346.8	356.0	364.5
157.5°	281.7	285.4	289.1	297.7	305.7	313.1	321.7	331.4	340.0	348.0	355.4
160°	285.7	288.8	292.0	298.8	305.7	311.4	318.3	326.3	333.7	340.0	346.2
162.5°	289.1	291.4	293.7	299.4	305.1	309.7	315.4	321.7	327.4	332.5	337.7
165°	291.4	293.1	294.8	300.0	304.0	307.4	311.4	316.5	321.1	325.1	329.1
167.5°	293.7	294.8	296.0	300.0	303.4	305.1	308.0	311.4	314.8	318.3	321.1
170°	294.8	295.6	296.5	299.4	302.3	303.4	305.1	307.4	310.3	312.0	314.3
172.5°	296.0	296.6	297.1	298.8	300.5	301.1	301.7	303.4	305.1	306.3	308.0
175°	296.5	296.8	297.1	298.3	299.4	298.8	299.4	300.0	301.7	302.3	302.8
177.5°	297.1	297.1	297.1	297.7	298.8	297.7	297.1	297.7	298.8	298.8	299.4
180°	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1

TEST NUMBER: P1010016

CATALOG NUMBER: S122RDIP-B485D530UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1024.4	1022.9	1018.4	1019.9	1017.7	1017.7	1016.2	1016.2	1016.2	1019.9	1017.7
5°	968.6	963.4	958.2	956.0	953.7	951.5	951.5	950.8	957.4	956.0	961.9
7.5°	899.4	897.9	887.5	887.5	883.8	882.3	886.0	886.8	887.5	889.0	892.7
10°	837.7	834.0	819.1	820.6	818.3	815.4	817.6	816.1	821.3	822.8	821.3
12.5°	764.8	758.1	741.7	733.5	724.6	717.9	726.1	720.1	741.0	746.9	763.3
15°	668.1	655.4	644.2	644.2	636.1	630.1	633.8	640.5	645.0	651.7	654.7
17.5°	603.3	598.1	589.2	584.0	581.8	579.5	579.5	582.5	592.2	591.4	597.4
20°	548.3	545.3	540.8	534.1	531.9	530.4	530.4	530.4	537.1	543.1	546.8
22.5°	510.3	508.1	505.1	496.2	491.7	490.3	494.0	496.2	501.4	505.9	509.6
25°	472.4	467.2	462.0	459.0	456.8	456.8	458.3	459.0	461.2	463.5	467.9
27.5°	441.2	437.4	430.0	421.8	421.8	419.6	421.1	422.6	427.8	435.2	438.9
30°	406.2	405.4	402.5	399.5	396.5	395.0	398.0	400.2	401.0	404.7	404.7
32.5°	380.9	375.7	370.5	367.5	366.0	365.3	366.0	369.0	369.0	373.5	378.7
35°	355.6	352.6	347.4	342.2	340.7	337.0	340.0	343.0	348.2	350.4	352.6
37.5°	328.1	324.4	322.1	320.6	317.7	318.4	316.2	320.6	325.1	324.4	325.8
40°	307.2	300.6	293.9	293.1	292.4	291.6	291.6	292.4	295.3	298.3	302.8
42.5°	280.5	278.2	272.3	266.3	264.8	263.4	261.9	264.8	270.8	276.0	278.2
45°	252.9	250.0	248.5	244.0	241.0	240.3	238.8	242.5	247.7	250.0	251.5
47.5°	227.6	226.9	222.4	223.2	220.9	221.7	220.9	223.2	223.2	225.4	226.9
50°	210.5	208.3	206.1	204.6	202.4	202.4	201.6	202.4	205.3	208.3	207.6
52.5°	193.4	189.7	189.0	188.2	186.7	188.2	186.0	186.7	189.7	191.2	190.4
55°	173.3	172.6	171.1	169.6	168.9	168.1	168.1	168.1	171.1	173.3	174.1
57.5°	157.7	154.0	151.0	151.0	148.0	147.3	148.8	149.5	151.8	153.3	154.7
60°	136.1	134.7	130.2	128.0	123.5	122.7	122.7	125.7	129.4	134.7	136.1
62.5°	113.1	110.8	110.1	110.1	110.1	110.1	110.1	110.1	110.1	110.8	110.8
65°	100.4	101.2	100.4	99.7	100.4	100.4	99.7	99.7	99.7	100.4	101.2
67.5°	90.0	89.3	90.0	89.3	88.5	88.5	87.8	88.5	89.3	90.0	90.0
70°	78.1	78.1	77.4	78.1	77.4	76.6	75.9	75.9	77.4	78.1	78.1
72.5°	67.0	67.0	66.2	66.2	64.7	64.7	65.5	64.7	64.7	67.0	67.0
75°	55.8	55.1	54.3	54.3	53.6	53.6	53.6	52.8	54.3	54.3	55.1
77.5°	43.9	43.9	43.9	43.1	43.1	42.4	42.4	43.1	43.1	43.1	43.9
80°	33.5	33.5	33.5	32.7	32.0	32.0	32.0	32.0	32.0	32.7	32.0
82.5°	23.1	23.1	23.1	23.1	23.1	22.3	22.3	22.3	23.1	23.1	22.3
85°	14.1	13.4	14.1	14.1	13.4	14.1	13.4	13.4	12.6	12.6	13.4
87.5°	6.0	5.2	4.5	4.5	5.2	4.5	4.5	4.5	5.2	4.5	4.5
90°	18.6	18.9	18.9	18.9	18.9	18.9	18.9	18.9	18.9	18.9	18.6
92.5°	40.6	38.3	37.7	35.4	36.0	34.9	36.0	35.4	37.7	38.3	40.6
95°	84.6	78.3	70.8	66.3	64.6	65.1	64.6	66.3	70.8	78.3	84.6
97.5°	169.7	152.6	130.3	118.8	112.6	109.1	112.6	118.8	130.3	152.6	169.7
100°	338.0	303.4	256.0	231.4	214.8	204.5	214.8	231.4	256.0	303.4	338.0
102.5°	571.4	534.2	481.7	435.4	413.7	398.8	413.7	435.4	481.7	534.2	571.4
105°	756.8	747.3	711.9	676.5	651.9	643.9	651.9	676.5	711.9	747.3	756.8
107.5°	823.9	835.3	834.8	829.6	822.2	809.1	822.2	829.6	834.8	835.3	823.9
110°	813.0	836.5	861.1	871.9	877.0	876.5	877.0	871.9	861.1	836.5	813.0

TEST NUMBER: P1010016

CATALOG NUMBER: S122RDIP-B485D530UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	776.2	803.9	840.5	860.5	871.3	875.3	871.3	860.5	840.5	803.9	776.2
115°	731.0	760.5	801.1	827.3	842.2	847.3	842.2	827.3	801.1	760.5	731.0
117.5°	687.9	715.9	757.6	785.6	801.1	805.1	801.1	785.6	757.6	715.9	687.9
120°	649.4	675.4	715.4	742.2	758.8	764.5	758.8	742.2	715.4	675.4	649.4
122.5°	619.4	642.2	677.1	703.4	717.6	722.2	717.6	703.4	677.1	642.2	619.4
125°	592.2	613.6	646.8	668.5	682.8	687.4	682.8	668.5	646.8	613.6	592.2
127.5°	569.1	589.1	618.2	638.8	651.4	654.8	651.4	638.8	618.2	589.1	569.1
130°	545.6	564.5	592.5	611.9	623.4	627.9	623.4	611.9	592.5	564.5	545.6
132.5°	521.3	538.8	566.2	585.7	595.9	599.9	595.9	585.7	566.2	538.8	521.3
135°	497.7	513.7	538.2	557.1	567.4	569.7	567.4	557.1	538.2	513.7	497.7
137.5°	473.6	487.9	511.4	527.9	537.1	540.5	537.1	527.9	511.4	487.9	473.6
140°	452.6	465.1	483.4	498.2	506.8	510.2	506.8	498.2	483.4	465.1	452.6
142.5°	432.2	442.2	459.4	472.5	479.9	479.9	479.9	472.5	459.4	442.2	432.2
145°	415.7	424.0	437.7	447.4	453.1	454.8	453.1	447.4	437.7	424.0	415.7
147.5°	401.1	407.4	419.4	427.4	431.4	432.5	431.4	427.4	419.4	407.4	401.1
150°	388.5	393.7	402.2	409.1	412.5	413.1	412.5	409.1	402.2	393.7	388.5
152.5°	378.0	382.2	388.5	394.2	396.5	396.5	396.5	394.2	388.5	382.2	378.0
155°	367.6	370.8	377.1	381.1	383.4	382.2	383.4	381.1	377.1	370.8	367.6
157.5°	358.0	360.5	365.1	368.5	369.7	369.7	369.7	368.5	365.1	360.5	358.0
160°	348.2	350.2	354.2	357.1	357.7	357.7	357.7	357.1	354.2	350.2	348.2
162.5°	339.1	340.5	344.5	346.2	346.8	346.2	346.8	346.2	344.5	340.5	339.1
165°	330.2	331.4	333.7	336.0	336.0	335.4	336.0	336.0	333.7	331.4	330.2
167.5°	322.2	323.4	324.5	325.7	325.7	325.1	325.7	325.7	324.5	323.4	322.2
170°	314.8	315.4	316.0	317.7	317.1	316.0	317.1	317.7	316.0	315.4	314.8
172.5°	308.2	308.5	309.1	309.7	309.1	308.5	309.1	309.7	309.1	308.5	308.2
175°	303.1	303.4	303.4	304.0	303.4	302.3	303.4	304.0	303.4	303.4	303.1
177.5°	299.4	299.4	299.4	299.4	298.8	297.7	298.8	299.4	299.4	299.4	299.4
180°	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1

TEST NUMBER: P1010016

CATALOG NUMBER: S122RDIP-B485D530UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1019.9	1023.7	1022.2	1014.0	1022.2	1024.4	1028.9	1033.3	1036.3	1040.8	1044.5
5°	956.0	963.4	967.9	963.4	978.3	980.5	990.9	996.9	1005.8	1013.2	1019.2
7.5°	895.7	901.7	910.6	912.1	921.0	931.4	946.3	961.2	975.3	982.7	989.4
10°	831.0	841.4	854.8	851.8	865.2	881.6	897.2	921.0	932.9	946.3	958.2
12.5°	766.3	773.0	790.8	796.8	816.1	828.7	850.3	865.2	895.0	910.6	921.0
15°	653.2	680.7	703.0	729.8	755.1	778.9	798.2	825.0	851.1	863.0	880.1
17.5°	601.8	614.5	627.9	641.3	674.0	716.4	750.6	779.6	802.0	817.6	837.7
20°	548.3	560.9	575.8	588.5	608.5	639.0	681.4	731.3	758.1	774.4	793.8
22.5°	510.3	522.2	531.9	543.1	558.7	581.0	613.0	674.8	710.5	730.5	747.7
25°	469.4	484.3	494.7	502.9	515.5	540.1	566.1	601.1	665.1	680.7	704.5
27.5°	441.2	445.6	457.5	470.2	482.8	496.2	523.0	552.7	595.9	630.1	659.1
30°	407.7	418.8	430.0	435.2	446.4	465.7	482.1	514.1	547.5	574.3	609.3
32.5°	382.4	389.1	396.5	409.2	419.6	433.0	449.3	476.1	504.4	521.5	548.3
35°	354.1	358.6	374.2	379.4	389.8	403.2	419.6	440.4	470.9	484.3	503.6
37.5°	327.3	337.7	342.2	354.1	363.8	377.2	389.1	412.9	433.0	448.6	466.4
40°	306.5	311.0	319.1	329.6	337.7	348.2	363.0	380.2	401.7	414.4	430.0
42.5°	281.2	284.9	295.3	301.3	314.7	324.4	333.3	354.1	373.5	383.1	398.8
45°	253.7	262.6	269.3	281.2	288.6	300.6	311.7	326.6	344.4	355.6	364.5
47.5°	229.9	238.8	245.5	256.7	268.6	273.8	285.7	301.3	317.7	326.6	339.2
50°	210.5	213.5	226.2	231.4	244.0	254.4	262.6	276.0	293.9	299.1	309.5
52.5°	191.9	194.2	202.4	209.0	220.2	229.1	239.5	252.2	267.1	275.3	283.4
55°	175.6	177.1	180.8	188.2	195.7	206.8	216.5	228.4	241.0	250.0	257.4
57.5°	157.0	159.9	162.9	167.4	174.8	185.2	195.7	206.8	217.2	223.2	232.9
60°	135.4	139.9	145.1	150.3	155.5	162.9	174.8	185.2	194.9	200.1	207.6
62.5°	112.3	121.3	125.7	131.7	136.1	142.8	151.8	163.7	170.4	177.1	183.0
65°	101.2	101.9	102.7	108.6	116.8	123.5	131.7	140.6	151.0	155.5	159.9
67.5°	90.0	90.8	92.2	93.0	96.0	103.4	112.3	122.0	130.2	133.2	137.6
70°	78.9	78.9	81.8	82.6	83.3	84.1	91.5	101.2	108.6	112.3	117.5
72.5°	67.0	67.7	69.2	69.9	71.4	72.9	75.1	80.3	89.3	93.0	98.9
75°	55.1	55.8	56.5	57.3	59.5	60.3	62.5	65.5	69.2	73.6	77.4
77.5°	43.9	43.9	44.6	46.1	47.6	48.4	50.6	52.1	53.6	55.8	58.8
80°	32.7	33.5	33.5	35.0	35.0	35.7	36.5	38.7	40.2	41.7	43.1
82.5°	22.3	23.8	23.8	23.8	24.5	25.3	26.0	26.0	27.5	28.3	30.5
85°	13.4	14.1	14.1	14.1	13.4	14.9	14.9	15.6	15.6	15.6	16.4
87.5°	5.2	4.5	5.2	5.2	5.2	6.0	5.2	5.2	6.0	6.7	6.7
90°	18.3	17.1	18.3	18.9	19.4	18.9	15.4	11.4	8.6	7.8	6.9
92.5°	42.9	49.1	57.7	73.7	88.0	86.8	67.4	45.7	30.3	27.2	24.0
95°	90.8	114.8	149.7	196.0	224.0	198.3	132.0	82.3	56.0	49.2	42.3
97.5°	186.8	244.5	306.3	368.0	365.1	282.3	175.4	106.3	72.6	64.8	57.1
100°	372.5	450.8	521.7	533.7	451.4	310.8	187.4	117.7	87.4	79.4	71.4
102.5°	608.5	660.5	662.8	595.4	454.2	300.0	188.0	128.0	100.6	92.6	84.6
105°	766.2	758.8	694.2	575.4	423.4	285.1	190.8	140.0	113.1	105.1	97.1
107.5°	812.5	756.5	660.5	533.1	394.8	277.1	197.1	152.0	125.7	117.7	109.7
110°	789.6	716.5	614.2	493.7	375.4	274.8	205.1	164.0	138.8	130.6	122.3

TEST NUMBER: P1010016

CATALOG NUMBER: S122RDIP-B485D530UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	748.5	669.1	571.9	466.2	362.8	275.4	213.7	175.4	151.4	142.9	134.3
115°	701.6	626.8	538.8	444.5	354.2	277.7	222.3	187.4	162.8	155.1	147.4
117.5°	659.9	590.2	511.4	429.7	349.7	281.1	231.4	198.3	175.4	167.4	159.4
120°	623.4	562.8	491.9	418.2	345.7	284.5	240.5	209.7	187.4	179.4	171.4
122.5°	596.5	539.9	476.5	408.5	343.4	288.5	248.5	220.5	200.0	191.7	183.4
125°	570.8	520.5	461.7	399.4	340.5	292.5	257.1	231.4	210.8	202.8	194.8
127.5°	549.1	501.1	446.8	390.8	338.8	296.5	265.1	241.7	221.7	213.4	205.1
130°	526.8	481.7	432.5	382.2	337.7	301.1	272.5	250.8	230.8	222.8	214.8
132.5°	503.9	463.4	418.8	375.4	337.1	305.7	280.0	258.8	240.0	232.0	224.0
135°	481.7	444.0	406.2	369.1	336.5	309.1	286.3	266.3	248.0	240.0	232.0
137.5°	459.4	428.5	396.0	364.5	336.5	312.5	291.4	272.5	254.3	246.8	239.4
140°	440.0	413.7	386.2	360.5	336.0	314.8	295.4	277.7	260.5	253.1	245.7
142.5°	422.2	400.5	378.2	356.5	336.0	316.5	298.8	281.7	265.1	258.2	251.4
145°	407.4	389.7	370.8	353.1	334.8	317.7	301.7	285.7	270.3	264.0	257.7
147.5°	394.8	380.5	365.1	349.7	333.1	318.3	303.4	289.1	274.3	268.6	262.8
150°	383.4	371.4	358.8	345.1	331.4	317.7	304.5	291.4	278.3	273.2	268.0
152.5°	373.7	364.0	352.5	341.1	328.5	316.5	305.1	293.7	282.3	277.7	273.1
155°	364.5	356.0	346.8	336.0	325.1	315.4	305.7	296.0	286.3	282.0	277.7
157.5°	355.4	348.0	340.0	331.4	321.7	313.1	305.7	297.7	289.1	285.4	281.7
160°	346.2	340.0	333.7	326.3	318.3	311.4	305.7	298.8	292.0	288.8	285.7
162.5°	337.7	332.5	327.4	321.7	315.4	309.7	305.1	299.4	293.7	291.4	289.1
165°	329.1	325.1	321.1	316.5	311.4	307.4	304.0	300.0	294.8	293.1	291.4
167.5°	321.1	318.3	314.8	311.4	308.0	305.1	303.4	300.0	296.0	294.8	293.7
170°	314.3	312.0	310.3	307.4	305.1	303.4	302.3	299.4	296.5	295.6	294.8
172.5°	308.0	306.3	305.1	303.4	301.7	301.1	300.5	298.8	297.1	296.6	296.0
175°	302.8	302.3	301.7	300.0	299.4	298.8	299.4	298.3	297.1	296.8	296.5
177.5°	299.4	298.8	298.8	297.7	297.1	297.7	298.8	297.7	297.1	297.1	297.1
180°	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1	297.1

TEST NUMBER: P1010016

CATALOG NUMBER: S122RDIP-B485D530UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1070.5	1070.5	1070.5	1070.5
2.5°	1051.2	1049.0	1062.3	1077.2
5°	1029.6	1033.3	1050.4	1071.3
7.5°	1007.3	1015.5	1035.6	1063.1
10°	976.0	990.9	1021.4	1049.7
12.5°	945.5	965.6	994.6	1028.1
15°	911.3	933.6	969.3	1009.5
17.5°	873.4	898.7	940.3	984.2
20°	833.2	866.7	910.6	958.2
22.5°	788.6	828.7	874.1	926.9
25°	745.4	789.3	834.7	895.7
27.5°	703.0	746.2	796.8	858.5
30°	660.6	700.0	754.4	820.6
32.5°	615.2	656.2	713.4	781.1
35°	573.6	614.5	668.1	735.0
37.5°	528.9	572.8	624.2	693.3
40°	476.9	528.2	578.0	644.2
42.5°	433.7	488.0	536.4	598.9
45°	399.5	450.8	491.0	552.0
47.5°	367.5	409.2	450.1	506.6
50°	337.0	369.0	411.4	462.0
52.5°	305.8	333.3	369.7	417.3
55°	277.5	303.5	336.3	372.7
57.5°	251.5	270.0	302.8	335.5
60°	222.4	241.8	267.1	294.6
62.5°	197.9	212.8	236.6	259.6
65°	171.8	186.0	203.8	225.4
67.5°	148.0	160.7	174.8	191.9
70°	126.5	136.1	146.6	161.4
72.5°	103.4	113.8	123.5	135.4
75°	84.8	89.3	97.5	105.6
77.5°	65.5	71.4	75.9	82.6
80°	46.9	52.1	53.6	58.8
82.5°	31.2	34.2	37.2	38.7
85°	17.9	19.3	22.3	23.1
87.5°	6.7	7.4	8.9	10.4
90°	5.7	4.6	2.3	0.6
92.5°	19.4	16.6	12.0	8.6
95°	33.1	28.0	22.3	20.0
97.5°	46.9	39.4	33.1	29.7
100°	60.0	50.9	45.7	44.0
102.5°	72.6	63.4	58.3	57.1
105°	84.6	76.0	72.0	69.7
107.5°	97.1	89.1	85.1	83.4
110°	110.3	102.8	99.4	97.1

TEST NUMBER: P1010016

CATALOG NUMBER: S122RDIP-B485D530UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	122.8	116.0	112.0	109.7
115°	136.0	129.1	125.7	122.8
117.5°	148.6	142.3	138.8	136.6
120°	160.0	154.8	151.4	149.1
122.5°	172.0	166.3	162.8	161.1
125°	183.4	176.6	173.1	171.4
127.5°	194.3	186.8	182.3	180.0
130°	203.4	195.4	189.7	187.4
132.5°	212.0	203.4	197.1	194.3
135°	218.8	210.3	203.4	201.1
137.5°	226.3	217.1	210.3	207.4
140°	233.1	224.0	217.1	214.8
142.5°	239.4	230.3	224.0	222.3
145°	246.3	237.7	232.0	229.7
147.5°	253.1	245.1	239.4	237.7
150°	259.4	252.0	247.4	245.7
152.5°	265.1	258.8	254.3	253.7
155°	271.4	265.1	261.7	261.1
157.5°	276.5	270.8	268.0	267.4
160°	281.1	276.5	274.3	273.7
162.5°	285.1	281.7	279.4	280.0
165°	288.5	285.1	284.0	284.5
167.5°	291.4	289.1	288.0	288.5
170°	293.7	292.0	291.4	292.5
172.5°	295.4	293.7	294.3	294.8
175°	296.5	295.4	296.0	296.5
177.5°	297.1	296.0	296.5	297.7
180°	297.1	297.1	297.1	297.1

(END OF REPORT)