

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010034

Luminaire Tested: S122RDIP-B485D530UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010034
REPORT IS A COMBINATION OF REPORTS P988334 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B485D530UB50-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3770.0 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010034

CATALOG NUMBER: S122RDIP-B485D530UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1010034

CATALOG NUMBER: S122RDIP-B485D530UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54
1	98	94	90	87	90	86	83	81	73	71	69	60	59	57	48	47	47
2	90	83	77	72	82	77	72	67	65	61	58	54	51	49	44	42	40
3	82	74	67	61	76	68	62	57	58	53	50	48	45	42	39	37	35
4	76	66	58	53	70	61	54	49	52	47	43	44	40	37	36	33	31
5	70	59	51	46	64	55	48	43	47	42	38	40	36	33	33	30	28
6	65	53	46	40	59	50	43	38	43	37	33	36	32	29	30	27	25
7	60	48	41	35	55	45	38	34	39	34	30	33	29	26	28	25	23
8	56	44	37	32	52	41	35	30	36	31	27	31	27	24	26	23	21
9	52	41	33	29	48	38	31	27	33	28	24	28	24	22	24	21	19
10	49	37	30	26	45	35	29	25	31	26	22	26	22	20	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16287	16287	16287	16287
5°	16324	17299	16381	13820
10°	16144	18284	16259	11412
15°	15794	18290	16062	8573
20°	15373	15118	15707	7073
25°	14861	9446	15182	6017
30°	14209	6048	14596	5181
35°	13416	4648	13851	4433
40°	12532	3907	13066	3878
45°	11586	3325	12071	3255
50°	10618	2826	11113	2816
55°	9545	2455	10059	2424
60°	8591	1872	9046	1850
65°	7700	1409	8159	1598
70°	6721	1125	7245	1302
75°	5678	861	6198	986
80°	4511	587	4854	645
85°	3136	303	3433	320

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 14898 cd/sqm

TEST NUMBER: P1010034

CATALOG NUMBER: S122RDIP-B485D530UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.6	2.6
10°-20°	272.4	7.2
20°-30°	350.6	9.3
30°-40°	332.6	8.8
40°-50°	285.0	7.6
50°-60°	217.1	5.8
60°-70°	136.9	3.6
70°-80°	68.3	1.8
80°-90°	19.4	0.5
90°-100°	111.4	3.0
100°-110°	392.3	10.4
110°-120°	412.0	10.9
120°-130°	339.0	9.0
130°-140°	272.3	7.2
140°-150°	205.7	5.5
150°-160°	144.6	3.8
160°-170°	85.1	2.3
170°-180°	27.7	0.7
0°-30°	720.6	19.1
0°-40°	1053.1	27.9
0°-60°	1555.3	41.3
0°-90°	1779.8	47.2
90°-120°	915.8	24.3
90°-150°	1732.7	46.0
90°-180°	1990.0	52.8
0°-180°	3770.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1029	1029	1029	1029	1029	
5°	1030	1145	1033	914	1030	98
15°	970	1292	987	606	970	273
25°	861	689	879	439	861	395
35°	706	340	729	324	706	442
45°	530	236	553	231	530	409
55°	358	164	378	162	358	323
65°	217	85	230	96	217	215
75°	102	45	111	52	102	110
85°	22	13	24	14	22	25
90°	0	18	0	18	0	3
95°	19	63	19	63	19	20
105°	67	619	67	619	67	71
115°	118	815	118	815	118	117
125°	165	661	165	661	165	147
135°	193	548	193	548	193	149
145°	221	438	221	438	221	139
155°	251	368	251	368	251	116
165°	274	323	274	323	274	77
175°	285	291	285	291	285	27
180°	286	286	286	286	286	

TEST NUMBER: P1010034

CATALOG NUMBER: S122RDIP-B485D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9
2.5°	1035.3	1039.6	1041.7	1044.6	1051.0	1055.3	1061.8	1063.2	1062.5	1065.3	1057.5
5°	1029.6	1038.9	1047.5	1054.6	1066.0	1073.2	1081.1	1090.3	1092.5	1103.2	1096.8
7.5°	1021.7	1035.3	1047.5	1061.8	1078.9	1088.2	1100.4	1114.7	1121.1	1134.0	1137.5
10°	1008.8	1028.1	1048.9	1063.9	1087.5	1103.9	1115.4	1138.3	1153.3	1172.6	1169.7
12.5°	988.1	1013.1	1041.0	1066.0	1096.8	1107.5	1129.0	1152.6	1171.9	1189.7	1205.5
15°	970.2	998.8	1029.6	1060.3	1095.4	1115.4	1136.8	1167.6	1188.3	1219.8	1233.3
17.5°	945.9	982.4	1018.9	1053.2	1094.6	1117.5	1144.0	1174.0	1204.7	1234.8	1245.5
20°	920.9	960.2	999.5	1046.0	1093.2	1115.4	1142.5	1179.7	1209.8	1233.3	1233.3
22.5°	890.9	938.8	983.8	1028.1	1079.6	1111.8	1139.7	1183.3	1204.7	1209.8	1190.4
25°	860.8	908.7	958.1	1013.1	1071.8	1100.4	1131.8	1172.6	1179.7	1159.7	1109.7
27.5°	825.1	878.7	934.5	993.8	1055.3	1091.1	1119.7	1146.8	1133.2	1079.6	1001.7
30°	788.6	846.5	909.5	965.9	1040.3	1073.2	1097.5	1105.4	1062.5	975.2	874.4
32.5°	750.7	807.2	873.7	941.6	1016.7	1048.2	1063.9	1043.2	964.5	854.4	731.4
35°	706.4	770.0	839.4	910.2	984.5	1008.1	1017.4	966.7	865.8	723.6	601.3
37.5°	666.4	730.0	804.4	876.6	948.8	961.7	952.4	873.0	745.0	604.2	484.8
40°	619.2	687.1	760.0	840.8	900.2	903.7	880.9	777.9	619.2	486.9	413.3
42.5°	575.6	644.2	717.1	799.4	844.4	832.2	801.5	666.4	516.9	419.7	360.4
45°	530.5	595.6	674.2	747.2	779.3	750.7	704.3	560.5	434.0	361.1	315.3
47.5°	486.9	547.7	625.6	695.7	701.4	669.2	614.2	469.7	376.1	317.5	280.3
50°	444.0	504.8	577.7	635.6	629.9	585.6	523.4	408.3	326.7	280.3	249.5
52.5°	401.1	456.2	526.9	572.7	548.4	505.5	444.0	346.1	285.3	244.5	220.9
55°	358.2	409.7	470.5	508.4	469.7	420.4	376.8	296.7	247.4	214.5	196.6
57.5°	322.5	363.2	419.0	441.9	395.4	356.8	318.9	255.2	214.5	190.9	170.2
60°	283.1	320.3	366.1	379.7	331.8	300.3	268.1	215.9	183.8	163.0	149.4
62.5°	249.5	280.3	315.3	315.3	273.1	249.5	225.2	180.9	154.4	138.0	131.6
65°	216.6	238.8	263.8	261.0	225.2	204.5	185.2	149.4	129.4	118.0	111.5
67.5°	184.5	201.6	218.1	208.1	182.3	164.4	146.6	120.8	107.2	99.4	90.8
70°	155.2	168.7	177.3	168.0	142.3	127.3	114.4	97.2	86.5	76.5	71.5
72.5°	130.1	135.8	138.7	127.3	105.8	97.2	87.9	75.8	66.5	61.5	60.1
75°	101.5	106.5	104.4	95.8	77.9	71.5	64.3	55.8	53.6	50.8	49.3
77.5°	79.4	79.4	75.8	67.9	55.8	50.8	47.9	43.6	41.5	40.8	39.3
80°	56.5	55.8	53.6	45.0	37.9	35.0	35.0	32.2	31.5	30.0	30.0
82.5°	37.2	37.2	34.3	27.2	25.0	24.3	23.6	22.2	22.2	21.4	21.4
85°	22.2	20.7	17.2	15.0	14.3	14.3	13.6	12.9	13.6	12.9	12.9
87.5°	10.0	7.9	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7
90°	0.5	2.2	4.4	5.5	6.6	7.4	8.2	11.0	14.8	18.1	18.7
92.5°	8.2	11.5	15.9	18.7	23.1	26.1	29.1	44.0	64.8	83.5	84.6
95°	19.2	21.4	26.9	31.9	40.7	47.3	53.9	79.1	127.0	190.7	215.4
97.5°	28.6	31.9	37.9	45.1	55.0	62.4	69.8	102.2	168.7	271.5	351.2
100°	42.3	44.0	48.9	57.7	68.7	76.4	84.1	113.2	180.3	299.0	434.2
102.5°	55.0	56.1	61.0	69.8	81.3	89.0	96.7	123.1	180.8	288.5	436.9
105°	67.0	69.2	73.1	81.3	93.4	101.1	108.8	134.6	183.6	274.2	407.2
107.5°	80.2	81.9	85.7	93.4	105.5	113.2	120.9	146.2	189.6	266.5	379.8
110°	93.4	95.6	98.9	106.1	117.6	125.6	133.5	157.7	197.3	264.3	361.1

TEST NUMBER: P1010034

CATALOG NUMBER: S122RDIP-B485D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	105.5	107.7	111.6	118.2	129.1	137.4	145.6	168.7	205.5	264.9	349.0
115°	118.2	120.9	124.2	130.8	141.8	149.2	156.6	180.3	213.8	267.1	340.7
117.5°	131.3	133.5	136.8	142.9	153.3	161.0	168.7	190.7	222.6	270.4	336.3
120°	143.4	145.6	148.9	153.9	164.9	172.6	180.3	201.7	231.4	273.7	332.5
122.5°	155.0	156.6	159.9	165.4	176.4	184.4	192.4	212.1	239.1	277.5	330.3
125°	164.9	166.5	169.8	176.4	187.4	195.1	202.8	222.6	247.3	281.4	327.5
127.5°	173.1	175.3	179.7	186.9	197.3	205.2	213.2	232.5	255.0	285.2	325.9
130°	180.3	182.5	188.0	195.6	206.6	214.3	222.0	241.3	262.1	289.6	324.8
132.5°	186.9	189.6	195.6	203.9	215.4	223.1	230.8	249.0	269.3	294.0	324.2
135°	193.4	195.6	202.2	210.5	223.1	230.8	238.5	256.1	275.3	297.3	323.7
137.5°	199.5	202.2	208.8	217.6	230.3	237.4	244.6	262.1	280.3	300.6	323.7
140°	206.6	208.8	215.4	224.2	236.3	243.4	250.6	267.1	284.1	302.8	323.1
142.5°	213.8	215.4	221.5	230.3	241.8	248.4	255.0	270.9	287.4	304.5	323.1
145°	220.9	223.1	228.6	236.9	247.9	253.9	259.9	274.8	290.2	305.6	322.0
147.5°	228.6	230.3	235.8	243.5	252.8	258.3	263.8	278.1	291.8	306.1	320.4
150°	236.3	238.0	242.4	249.5	257.7	262.6	267.6	280.3	292.9	305.6	318.8
152.5°	244.0	244.6	249.0	255.0	262.7	267.1	271.5	282.5	293.5	304.5	316.0
155°	251.2	251.7	255.0	261.0	267.1	271.2	275.3	284.7	294.0	303.4	312.7
157.5°	257.2	257.7	260.5	266.0	270.9	274.5	278.1	286.3	294.0	301.2	309.4
160°	263.2	263.8	266.0	270.4	274.8	277.8	280.8	287.4	294.0	299.5	306.1
162.5°	269.3	268.7	270.9	274.2	278.1	280.3	282.5	288.0	293.5	297.9	303.4
165°	273.7	273.1	274.2	277.5	280.3	282.0	283.6	288.5	292.4	295.7	299.5
167.5°	277.5	277.0	278.1	280.3	282.5	283.6	284.7	288.5	291.8	293.5	296.2
170°	281.4	280.3	280.8	282.5	283.6	284.4	285.2	288.0	290.7	291.8	293.5
172.5°	283.6	283.0	282.5	284.1	284.7	285.2	285.8	287.4	289.1	289.6	290.2
175°	285.2	284.7	284.1	285.2	285.2	285.5	285.8	286.9	288.0	287.4	288.0
177.5°	286.3	285.2	284.7	285.8	285.8	285.8	285.8	286.3	287.4	286.3	285.8
180°	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8

TEST NUMBER: P1010034

CATALOG NUMBER: S122RDIP-B485D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9
2.5°	1065.3	1066.8	1068.9	1078.9	1080.3	1083.2	1081.8	1081.8	1082.5	1081.1	1081.8
5°	1111.1	1113.2	1124.0	1136.1	1139.0	1136.1	1139.7	1144.7	1144.7	1144.7	1143.3
7.5°	1154.0	1161.8	1174.0	1191.9	1195.5	1199.0	1205.5	1201.2	1202.6	1209.0	1206.9
10°	1195.5	1206.9	1220.5	1235.5	1243.4	1248.4	1251.2	1257.7	1272.7	1255.5	1261.9
12.5°	1234.8	1251.2	1265.5	1282.0	1287.7	1294.1	1296.3	1302.0	1302.0	1301.3	1306.3
15°	1260.5	1275.5	1288.4	1299.1	1300.6	1299.1	1297.7	1298.4	1300.6	1292.0	1297.0
17.5°	1266.2	1267.7	1272.0	1267.7	1268.4	1253.4	1244.8	1242.6	1222.6	1223.3	1239.8
20°	1238.4	1214.0	1207.6	1184.0	1169.7	1131.1	1129.7	1118.9	1076.8	1089.6	1086.8
22.5°	1161.8	1120.4	1065.3	1038.2	1024.6	983.8	952.4	930.2	915.2	900.2	893.7
25°	1061.0	993.8	915.9	862.3	854.4	816.5	758.6	731.4	699.3	689.2	706.4
27.5°	930.9	843.7	755.7	673.5	658.5	624.2	594.9	575.6	538.4	536.2	537.7
30°	754.3	666.4	592.7	539.1	501.9	486.2	466.9	452.6	437.6	443.3	444.7
32.5°	619.9	536.2	467.6	439.0	421.8	411.8	395.4	386.1	379.7	377.5	376.8
35°	492.6	436.9	406.1	378.2	368.2	361.1	348.9	344.6	338.9	339.6	339.6
37.5°	421.8	375.4	352.5	338.2	328.9	325.3	317.5	313.2	309.6	308.2	310.3
40°	363.9	331.8	317.5	304.6	296.7	295.3	291.0	286.0	281.7	282.4	284.6
42.5°	321.7	303.2	286.0	276.0	270.3	268.1	264.5	261.0	261.0	258.8	258.1
45°	288.1	273.1	258.8	249.5	246.0	243.1	238.8	238.1	235.2	235.9	236.7
47.5°	258.1	246.0	235.2	225.9	222.4	221.6	217.4	214.5	214.5	213.8	213.1
50°	230.9	218.8	209.5	204.5	199.5	198.1	197.3	196.6	195.2	195.2	195.9
52.5°	208.8	196.6	189.5	185.2	182.3	180.9	180.9	180.2	180.2	180.2	179.5
55°	184.5	174.5	168.7	167.3	165.9	165.2	164.4	163.0	162.3	163.7	162.3
57.5°	161.6	158.0	153.0	151.6	148.0	148.0	145.9	144.4	143.0	144.4	144.4
60°	143.7	138.7	135.8	131.6	128.7	125.8	122.3	121.5	120.1	119.4	118.7
62.5°	125.1	120.8	113.7	107.2	103.0	100.1	98.7	98.0	98.0	97.2	97.2
65°	104.4	94.4	90.8	88.7	87.9	87.2	85.8	85.1	85.8	85.1	85.8
67.5°	81.5	80.1	77.9	76.5	75.8	75.1	75.1	74.4	74.4	74.4	74.4
70°	70.8	67.2	66.5	65.1	65.1	64.3	64.3	64.3	64.3	63.6	65.1
72.5°	58.6	56.5	55.8	55.1	55.1	55.1	54.3	54.3	54.3	53.6	54.3
75°	47.9	47.2	45.8	45.8	45.0	45.8	45.0	45.0	44.3	45.0	45.0
77.5°	38.6	37.9	37.2	37.2	36.5	36.5	36.5	36.5	36.5	36.5	37.2
80°	29.3	28.6	27.9	28.6	27.9	28.6	27.9	27.9	28.6	27.9	27.9
82.5°	21.4	20.7	20.7	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0
85°	12.9	12.2	12.2	12.9	12.2	12.9	12.2	12.2	12.2	12.9	12.9
87.5°	5.7	6.4	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	6.4
90°	18.1	17.6	16.5	17.6	17.8	18.1	18.1	18.1	18.1	18.1	18.1
92.5°	70.9	55.5	47.3	41.2	39.0	36.8	36.3	34.1	34.6	33.5	34.6
95°	188.5	144.0	110.5	87.4	81.4	75.3	68.1	63.8	62.1	62.7	62.1
97.5°	353.9	294.6	235.2	179.7	163.2	146.7	125.3	114.3	108.3	105.0	108.3
100°	513.3	501.8	433.6	358.3	325.0	291.8	246.2	222.6	206.6	196.7	206.6
102.5°	572.7	637.5	635.3	585.3	549.6	513.9	463.3	418.8	397.9	383.6	397.9
105°	553.4	667.7	729.8	737.0	727.9	718.8	684.8	650.7	627.1	619.4	627.1
107.5°	512.8	635.3	727.6	781.5	792.5	803.5	802.9	798.0	790.8	778.2	790.8
110°	474.8	590.8	689.2	759.5	782.0	804.6	828.2	838.6	843.6	843.0	843.6

TEST NUMBER: P1010034

CATALOG NUMBER: S122RDIP-B485D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	448.5	550.1	643.5	719.9	746.6	773.2	808.4	827.7	838.1	841.9	838.1
115°	427.6	518.2	602.9	674.9	703.2	731.5	770.5	795.8	810.1	815.0	810.1
117.5°	413.3	491.9	567.7	634.8	661.7	688.6	728.7	755.7	770.5	774.3	770.5
120°	402.3	473.2	541.3	599.6	624.6	649.6	688.1	713.9	729.8	735.3	729.8
122.5°	392.9	458.3	519.3	573.8	595.8	617.7	651.2	676.5	690.3	694.7	690.3
125°	384.2	444.1	500.7	549.0	569.6	590.2	622.1	643.0	656.7	661.1	656.7
127.5°	375.9	429.8	482.0	528.1	547.4	566.6	594.6	614.4	626.5	629.8	626.5
130°	367.7	416.0	463.3	506.7	524.8	543.0	569.9	588.6	599.6	604.0	599.6
132.5°	361.1	402.8	445.7	484.7	501.4	518.2	544.6	563.3	573.2	577.1	573.2
135°	355.0	390.7	427.0	463.3	478.7	494.1	517.7	535.8	545.7	547.9	545.7
137.5°	350.6	380.9	412.2	441.9	455.6	469.3	491.9	507.8	516.6	519.9	516.6
140°	346.8	371.5	397.9	423.2	435.3	447.4	464.9	479.2	487.5	490.8	487.5
142.5°	342.9	363.8	385.3	406.1	415.8	425.4	441.9	454.5	461.6	461.6	461.6
145°	339.6	356.7	374.8	391.8	399.8	407.8	421.0	430.3	435.8	437.5	435.8
147.5°	336.3	351.2	366.0	379.8	385.8	391.8	403.4	411.1	414.9	416.0	414.9
150°	331.9	345.1	357.2	368.8	373.8	378.7	386.9	393.5	396.8	397.3	396.8
152.5°	328.1	339.1	350.1	359.4	363.5	367.7	373.7	379.2	381.4	381.4	381.4
155°	323.1	333.6	342.4	350.6	353.6	356.7	362.7	366.6	368.8	367.7	368.8
157.5°	318.8	327.0	334.7	341.8	344.3	346.8	351.2	354.5	355.6	355.6	355.6
160°	313.8	321.0	327.0	333.0	335.0	336.9	340.7	343.5	344.0	344.0	344.0
162.5°	309.4	314.9	319.9	324.8	326.2	327.5	331.4	333.0	333.6	333.0	333.6
165°	304.5	308.9	312.7	316.6	317.7	318.8	321.0	323.1	323.1	322.6	323.1
167.5°	299.5	302.8	306.1	308.9	310.0	311.1	312.2	313.3	313.3	312.7	313.3
170°	295.7	298.4	300.1	302.3	302.8	303.4	303.9	305.6	305.0	303.9	305.0
172.5°	291.8	293.5	294.6	296.2	296.5	296.8	297.3	297.9	297.3	296.8	297.3
175°	288.5	290.2	290.7	291.3	291.6	291.8	291.8	292.4	291.8	290.7	291.8
177.5°	286.3	287.4	287.4	288.0	288.0	288.0	288.0	288.0	287.4	286.3	287.4
180°	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8

TEST NUMBER: P1010034

CATALOG NUMBER: S122RDIP-B485D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9
2.5°	1084.6	1079.6	1078.2	1079.6	1078.2	1078.9	1073.9	1055.3	1060.3	1052.5	1056.7
5°	1146.1	1141.8	1132.5	1131.1	1129.7	1128.2	1121.1	1104.6	1098.2	1087.5	1086.8
7.5°	1204.7	1204.7	1197.6	1192.6	1186.2	1181.2	1171.9	1147.5	1137.5	1124.7	1117.5
10°	1262.7	1244.1	1251.9	1246.9	1231.2	1228.3	1211.2	1196.9	1177.6	1164.7	1153.3
12.5°	1304.1	1298.4	1291.3	1287.0	1282.7	1273.4	1261.9	1225.5	1215.5	1189.7	1176.9
15°	1302.7	1299.1	1301.3	1301.3	1299.8	1297.7	1288.4	1261.9	1244.8	1219.8	1197.6
17.5°	1232.6	1241.9	1251.2	1257.7	1272.0	1278.4	1287.0	1271.2	1260.5	1239.1	1215.5
20°	1110.4	1133.2	1160.4	1166.1	1179.0	1216.9	1234.1	1247.6	1251.9	1244.8	1225.5
22.5°	940.2	959.5	1025.3	1023.9	1042.4	1087.5	1137.5	1178.3	1210.5	1228.3	1221.2
25°	736.4	763.6	798.6	825.1	885.9	953.1	1015.3	1080.3	1136.1	1185.4	1197.6
27.5°	557.0	592.7	620.6	655.6	686.4	765.7	845.8	947.4	1012.4	1106.1	1154.7
30°	450.4	466.9	494.8	511.2	526.2	587.0	677.8	777.9	892.3	1000.3	1083.9
32.5°	384.7	396.1	416.8	424.0	439.7	480.5	537.7	629.2	747.2	878.0	988.1
35°	345.3	357.5	361.8	368.2	381.1	406.8	446.1	512.6	619.2	747.2	878.7
37.5°	311.7	318.2	330.3	334.6	338.9	358.2	384.7	431.1	501.9	607.0	752.9
40°	288.1	291.7	298.1	301.7	304.6	318.2	341.8	373.2	425.4	505.5	639.9
42.5°	263.1	267.4	271.7	276.0	279.6	290.3	304.6	334.6	369.6	430.4	527.7
45°	238.8	241.7	246.7	249.5	254.5	263.1	276.0	296.7	328.2	366.8	445.4
47.5°	216.6	220.2	222.4	225.9	229.5	238.8	251.0	264.5	290.3	328.2	385.4
50°	196.6	200.9	203.8	204.5	207.3	215.9	225.9	240.9	257.4	286.7	336.8
52.5°	182.3	183.0	185.2	188.0	187.3	192.3	201.6	213.1	230.2	253.8	290.3
55°	165.9	168.0	169.5	170.2	170.2	174.5	179.5	190.2	203.8	223.1	253.8
57.5°	145.1	147.3	151.6	153.0	155.2	157.3	159.4	166.6	178.0	196.6	221.6
60°	123.7	125.1	129.4	132.3	133.7	139.4	142.3	148.0	154.4	168.0	191.6
62.5°	99.4	100.8	103.0	105.8	108.7	117.3	124.4	130.1	135.1	144.4	163.7
65°	86.5	87.2	88.7	89.4	90.1	93.7	100.1	108.0	117.3	124.4	135.8
67.5°	75.1	75.8	76.5	77.9	78.6	79.4	82.2	84.4	93.7	103.7	112.3
70°	64.3	65.8	66.5	66.5	67.2	68.6	70.1	72.9	75.8	80.8	91.5
72.5°	54.3	55.1	56.5	56.5	56.5	57.9	59.3	60.8	62.2	65.1	69.4
75°	45.0	46.5	46.5	46.5	47.2	47.2	48.6	50.0	51.5	53.6	55.1
77.5°	37.2	37.2	37.2	37.2	37.9	37.9	38.6	40.0	40.8	41.5	42.9
80°	27.9	28.6	28.6	28.6	29.3	29.3	29.3	30.7	31.5	31.5	32.9
82.5°	20.7	20.7	20.7	21.4	20.7	21.4	21.4	22.2	21.4	22.2	22.9
85°	12.9	12.9	12.9	13.6	13.6	13.6	13.6	13.6	13.6	13.6	14.3
87.5°	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	7.1	6.4	6.4
90°	18.1	18.1	18.1	17.8	17.6	16.5	17.6	18.1	18.7	18.1	14.8
92.5°	34.1	36.3	36.8	39.0	41.2	47.3	55.5	70.9	84.6	83.5	64.8
95°	63.8	68.1	75.3	81.4	87.4	110.5	144.0	188.5	215.4	190.7	127.0
97.5°	114.3	125.3	146.7	163.2	179.7	235.2	294.6	353.9	351.2	271.5	168.7
100°	222.6	246.2	291.8	325.0	358.3	433.6	501.8	513.3	434.2	299.0	180.3
102.5°	418.8	463.3	513.9	549.6	585.3	635.3	637.5	572.7	436.9	288.5	180.8
105°	650.7	684.8	718.8	727.9	737.0	729.8	667.7	553.4	407.2	274.2	183.6
107.5°	798.0	802.9	803.5	792.5	781.5	727.6	635.3	512.8	379.8	266.5	189.6
110°	838.6	828.2	804.6	782.0	759.5	689.2	590.8	474.8	361.1	264.3	197.3

TEST NUMBER: P1010034

CATALOG NUMBER: S122RDIP-B485D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	827.7	808.4	773.2	746.6	719.9	643.5	550.1	448.5	349.0	264.9	205.5
115°	795.8	770.5	731.5	703.2	674.9	602.9	518.2	427.6	340.7	267.1	213.8
117.5°	755.7	728.7	688.6	661.7	634.8	567.7	491.9	413.3	336.3	270.4	222.6
120°	713.9	688.1	649.6	624.6	599.6	541.3	473.2	402.3	332.5	273.7	231.4
122.5°	676.5	651.2	617.7	595.8	573.8	519.3	458.3	392.9	330.3	277.5	239.1
125°	643.0	622.1	590.2	569.6	549.0	500.7	444.1	384.2	327.5	281.4	247.3
127.5°	614.4	594.6	566.6	547.4	528.1	482.0	429.8	375.9	325.9	285.2	255.0
130°	588.6	569.9	543.0	524.8	506.7	463.3	416.0	367.7	324.8	289.6	262.1
132.5°	563.3	544.6	518.2	501.4	484.7	445.7	402.8	361.1	324.2	294.0	269.3
135°	535.8	517.7	494.1	478.7	463.3	427.0	390.7	355.0	323.7	297.3	275.3
137.5°	507.8	491.9	469.3	455.6	441.9	412.2	380.9	350.6	323.7	300.6	280.3
140°	479.2	464.9	447.4	435.3	423.2	397.9	371.5	346.8	323.1	302.8	284.1
142.5°	454.5	441.9	425.4	415.8	406.1	385.3	363.8	342.9	323.1	304.5	287.4
145°	430.3	421.0	407.8	399.8	391.8	374.8	356.7	339.6	322.0	305.6	290.2
147.5°	411.1	403.4	391.8	385.8	379.8	366.0	351.2	336.3	320.4	306.1	291.8
150°	393.5	386.9	378.7	373.8	368.8	357.2	345.1	331.9	318.8	305.6	292.9
152.5°	379.2	373.7	367.7	363.5	359.4	350.1	339.1	328.1	316.0	304.5	293.5
155°	366.6	362.7	356.7	353.6	350.6	342.4	333.6	323.1	312.7	303.4	294.0
157.5°	354.5	351.2	346.8	344.3	341.8	334.7	327.0	318.8	309.4	301.2	294.0
160°	343.5	340.7	336.9	335.0	333.0	327.0	321.0	313.8	306.1	299.5	294.0
162.5°	333.0	331.4	327.5	326.2	324.8	319.9	314.9	309.4	303.4	297.9	293.5
165°	323.1	321.0	318.8	317.7	316.6	312.7	308.9	304.5	299.5	295.7	292.4
167.5°	313.3	312.2	311.1	310.0	308.9	306.1	302.8	299.5	296.2	293.5	291.8
170°	305.6	303.9	303.4	302.8	302.3	300.1	298.4	295.7	293.5	291.8	290.7
172.5°	297.9	297.3	296.8	296.5	296.2	294.6	293.5	291.8	290.2	289.6	289.1
175°	292.4	291.8	291.8	291.6	291.3	290.7	290.2	288.5	288.0	287.4	288.0
177.5°	288.0	288.0	288.0	288.0	288.0	287.4	287.4	286.3	285.8	286.3	287.4
180°	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8

TEST NUMBER: P1010034

CATALOG NUMBER: S122RDIP-B485D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9
2.5°	1050.3	1046.7	1046.7	1044.6	1044.6	1033.2	1033.2	1036.7	1032.4	1027.4	1020.3
5°	1077.5	1069.6	1067.5	1064.6	1055.3	1041.0	1035.3	1033.2	1024.6	1013.8	1001.7
7.5°	1103.2	1090.3	1083.9	1077.5	1065.3	1045.3	1033.9	1026.0	1013.1	996.7	981.0
10°	1128.2	1111.8	1095.4	1087.5	1070.3	1045.3	1028.9	1016.0	997.4	975.2	953.1
12.5°	1151.1	1116.8	1113.9	1098.2	1073.2	1044.6	1019.6	1001.0	977.4	951.6	925.9
15°	1171.1	1136.1	1118.9	1104.6	1071.8	1036.0	1009.6	986.7	955.2	925.9	894.4
17.5°	1181.2	1143.3	1131.8	1108.2	1074.6	1028.1	992.4	964.5	930.2	895.2	859.4
20°	1191.2	1146.8	1128.2	1111.8	1066.0	1013.1	973.1	940.9	903.0	861.6	822.2
22.5°	1196.2	1146.8	1124.7	1101.8	1057.5	996.7	949.5	911.6	867.3	825.1	777.9
25°	1187.6	1142.5	1116.1	1092.5	1042.4	976.7	922.3	879.4	832.2	784.3	736.4
27.5°	1166.1	1132.5	1101.8	1077.5	1021.7	950.9	893.7	845.1	796.5	742.9	694.2
30°	1126.1	1111.1	1086.8	1059.6	998.8	928.0	860.1	810.1	756.5	702.8	652.1
32.5°	1063.9	1076.8	1061.0	1037.4	971.7	896.6	824.4	773.6	715.0	657.1	610.6
35°	988.1	1033.9	1025.3	1008.8	943.1	863.0	790.8	729.3	670.7	612.0	565.6
37.5°	905.2	974.5	981.7	971.7	910.2	828.7	749.3	689.2	629.2	569.8	522.7
40°	791.5	898.0	920.9	925.2	875.9	787.2	704.3	645.6	586.3	528.4	471.2
42.5°	687.1	821.5	850.1	868.0	832.2	746.4	662.8	597.7	539.1	486.9	429.7
45°	589.1	729.3	775.8	798.6	782.9	700.0	613.5	552.7	499.1	451.2	396.1
47.5°	488.3	629.2	694.2	730.7	730.7	652.8	566.3	506.2	454.7	414.0	365.4
50°	421.1	538.4	605.6	653.5	666.4	604.9	523.4	464.7	416.1	371.8	334.6
52.5°	358.9	464.0	519.8	569.8	607.0	553.4	475.5	422.6	374.7	333.2	303.9
55°	310.3	389.0	439.7	494.8	536.2	501.2	429.0	377.5	336.0	301.7	276.7
57.5°	263.8	332.5	373.9	422.6	466.9	440.4	382.5	338.2	301.7	271.7	249.5
60°	224.5	280.3	312.4	350.3	405.4	386.8	338.9	298.1	268.8	241.7	223.1
62.5°	190.9	235.2	262.4	289.6	339.6	331.0	293.9	262.4	237.4	214.5	198.8
65°	156.6	193.0	214.5	238.1	278.1	281.7	251.7	229.5	206.6	186.6	172.3
67.5°	126.6	155.2	174.5	194.5	226.6	236.7	215.9	197.3	178.0	161.6	148.7
70°	102.2	122.3	136.6	152.3	178.7	190.9	180.2	167.3	151.6	138.0	126.6
72.5°	80.8	93.7	102.2	114.4	135.8	148.0	147.3	135.8	124.4	115.1	105.8
75°	59.3	69.4	76.5	84.4	101.5	113.0	115.8	110.8	99.4	92.2	85.1
77.5°	45.0	50.8	54.3	60.1	72.2	82.2	86.5	85.1	77.2	71.5	66.5
80°	34.3	35.7	37.2	39.3	49.3	58.6	61.5	60.8	56.5	54.3	48.6
82.5°	24.3	25.0	25.7	26.5	30.0	37.9	40.8	42.2	38.6	36.5	31.5
85°	14.3	15.0	15.0	16.4	17.2	19.3	24.3	24.3	23.6	20.7	20.0
87.5°	7.1	7.1	6.4	6.4	7.1	7.9	9.3	10.7	9.3	8.6	7.9
90°	11.0	8.2	7.4	6.6	5.5	4.4	2.2	0.5	2.2	4.4	5.5
92.5°	44.0	29.1	26.1	23.1	18.7	15.9	11.5	8.2	11.5	15.9	18.7
95°	79.1	53.9	47.3	40.7	31.9	26.9	21.4	19.2	21.4	26.9	31.9
97.5°	102.2	69.8	62.4	55.0	45.1	37.9	31.9	28.6	31.9	37.9	45.1
100°	113.2	84.1	76.4	68.7	57.7	48.9	44.0	42.3	44.0	48.9	57.7
102.5°	123.1	96.7	89.0	81.3	69.8	61.0	56.1	55.0	56.1	61.0	69.8
105°	134.6	108.8	101.1	93.4	81.3	73.1	69.2	67.0	69.2	73.1	81.3
107.5°	146.2	120.9	113.2	105.5	93.4	85.7	81.9	80.2	81.9	85.7	93.4
110°	157.7	133.5	125.6	117.6	106.1	98.9	95.6	93.4	95.6	98.9	106.1

TEST NUMBER: P1010034

CATALOG NUMBER: S122RDIP-B485D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	168.7	145.6	137.4	129.1	118.2	111.6	107.7	105.5	107.7	111.6	118.2
115°	180.3	156.6	149.2	141.8	130.8	124.2	120.9	118.2	120.9	124.2	130.8
117.5°	190.7	168.7	161.0	153.3	142.9	136.8	133.5	131.3	133.5	136.8	142.9
120°	201.7	180.3	172.6	164.9	153.9	148.9	145.6	143.4	145.6	148.9	153.9
122.5°	212.1	192.4	184.4	176.4	165.4	159.9	156.6	155.0	156.6	159.9	165.4
125°	222.6	202.8	195.1	187.4	176.4	169.8	166.5	164.9	166.5	169.8	176.4
127.5°	232.5	213.2	205.2	197.3	186.9	179.7	175.3	173.1	175.3	179.7	186.9
130°	241.3	222.0	214.3	206.6	195.6	188.0	182.5	180.3	182.5	188.0	195.6
132.5°	249.0	230.8	223.1	215.4	203.9	195.6	189.6	186.9	189.6	195.6	203.9
135°	256.1	238.5	230.8	223.1	210.5	202.2	195.6	193.4	195.6	202.2	210.5
137.5°	262.1	244.6	237.4	230.3	217.6	208.8	202.2	199.5	202.2	208.8	217.6
140°	267.1	250.6	243.4	236.3	224.2	215.4	208.8	206.6	208.8	215.4	224.2
142.5°	270.9	255.0	248.4	241.8	230.3	221.5	215.4	213.8	215.4	221.5	230.3
145°	274.8	259.9	253.9	247.9	236.9	228.6	223.1	220.9	223.1	228.6	236.9
147.5°	278.1	263.8	258.3	252.8	243.5	235.8	230.3	228.6	230.3	235.8	243.5
150°	280.3	267.6	262.6	257.7	249.5	242.4	238.0	236.3	238.0	242.4	249.5
152.5°	282.5	271.5	267.1	262.7	255.0	249.0	244.6	244.0	244.6	249.0	255.0
155°	284.7	275.3	271.2	267.1	261.0	255.0	251.7	251.2	251.7	255.0	261.0
157.5°	286.3	278.1	274.5	270.9	266.0	260.5	257.7	257.2	257.7	260.5	266.0
160°	287.4	280.8	277.8	274.8	270.4	266.0	263.8	263.2	263.8	266.0	270.4
162.5°	288.0	282.5	280.3	278.1	274.2	270.9	268.7	269.3	268.7	270.9	274.2
165°	288.5	283.6	282.0	280.3	277.5	274.2	273.1	273.7	273.1	274.2	277.5
167.5°	288.5	284.7	283.6	282.5	280.3	278.1	277.0	277.5	277.0	278.1	280.3
170°	288.0	285.2	284.4	283.6	282.5	280.8	280.3	281.4	280.3	280.8	282.5
172.5°	287.4	285.8	285.2	284.7	284.1	282.5	283.0	283.6	283.0	282.5	284.1
175°	286.9	285.8	285.5	285.2	285.2	284.1	284.7	285.2	284.7	284.1	285.2
177.5°	286.3	285.8	285.8	285.8	285.8	284.7	285.2	286.3	285.2	284.7	285.8
180°	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8

TEST NUMBER: P1010034

CATALOG NUMBER: S122RDIP-B485D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9
2.5°	1017.4	1018.1	1020.3	1013.8	1003.8	999.5	986.7	984.5	982.4	982.4	984.5
5°	994.5	991.7	992.4	980.2	965.9	957.4	939.5	942.3	933.1	927.3	928.8
7.5°	969.5	961.7	960.9	945.2	927.3	911.6	893.0	888.7	880.1	870.1	865.8
10°	938.1	932.3	921.6	903.7	880.9	868.0	843.0	828.0	825.8	810.8	805.1
12.5°	905.9	895.9	885.1	860.1	834.4	813.7	795.1	778.6	767.2	754.3	745.7
15°	868.7	856.6	844.4	817.9	787.9	767.2	739.3	715.0	681.4	654.9	639.9
17.5°	828.0	814.4	797.9	768.6	739.3	710.7	659.2	630.6	607.0	591.3	582.0
20°	785.8	770.8	754.3	725.0	674.2	624.2	595.6	573.4	559.1	543.4	531.9
22.5°	741.4	725.7	707.8	662.1	608.5	573.4	551.3	530.5	509.8	501.2	495.5
25°	700.0	685.7	662.8	600.6	558.4	526.2	501.2	487.6	476.9	465.5	454.7
27.5°	657.1	630.6	598.4	546.2	519.8	486.9	469.0	459.0	440.4	432.6	427.6
30°	605.6	576.3	545.5	508.4	477.6	454.7	438.3	421.8	411.1	403.3	394.7
32.5°	553.4	525.5	506.2	467.6	444.7	421.1	405.4	395.4	379.7	374.7	371.1
35°	508.4	484.8	467.6	436.1	414.7	393.2	381.8	366.8	356.8	347.5	341.8
37.5°	464.0	451.2	433.3	406.8	383.9	366.8	351.1	346.1	332.5	327.5	321.7
40°	433.3	414.0	399.0	376.1	356.8	338.2	328.2	316.7	307.4	299.6	297.4
42.5°	396.1	381.8	373.2	348.2	328.2	317.5	305.3	292.4	285.3	278.8	271.0
45°	368.2	355.3	343.2	323.2	305.3	291.7	281.0	272.4	260.3	257.4	245.2
47.5°	338.9	326.0	316.7	296.7	280.3	267.4	259.5	248.1	238.1	231.7	225.9
50°	309.6	298.9	290.3	273.1	258.8	245.2	234.5	223.1	218.8	208.1	204.5
52.5°	281.7	274.6	265.3	248.8	234.5	223.1	211.6	202.3	195.9	190.2	185.9
55°	258.1	246.7	242.4	224.5	212.4	200.2	190.2	184.5	176.6	173.0	169.5
57.5°	231.7	225.2	218.1	204.5	190.9	179.5	172.3	163.7	159.4	155.2	152.3
60°	208.8	199.5	193.8	182.3	170.2	159.4	153.0	146.6	140.9	137.3	131.6
62.5°	182.3	175.2	171.6	159.4	149.4	139.4	133.7	127.3	123.0	116.5	109.4
65°	159.4	153.7	149.4	139.4	130.1	120.8	115.1	107.2	101.5	98.0	97.2
67.5°	139.4	135.1	128.7	119.4	110.1	103.0	96.5	90.1	89.4	87.9	87.9
70°	117.3	113.0	109.4	99.4	91.5	83.7	82.2	80.1	77.9	77.2	75.8
72.5°	98.0	94.4	90.1	81.5	73.6	71.5	70.1	68.6	66.5	65.8	65.1
75°	79.4	74.4	71.5	63.6	61.5	60.1	58.6	56.5	55.1	54.3	52.9
77.5°	60.8	55.8	55.8	51.5	50.0	47.9	46.5	45.0	44.3	42.9	42.9
80°	42.9	42.9	41.5	39.3	37.2	36.5	34.3	33.6	32.9	33.6	32.2
82.5°	31.5	28.6	28.6	27.2	25.7	25.0	23.6	23.6	22.9	22.9	22.9
85°	17.9	17.9	17.2	15.7	15.0	15.0	14.3	14.3	13.6	13.6	12.9
87.5°	7.1	6.4	7.1	6.4	6.4	5.7	5.7	5.7	5.0	5.7	5.0
90°	6.6	7.4	8.2	11.0	14.8	18.1	18.7	18.1	17.6	16.5	17.6
92.5°	23.1	26.1	29.1	44.0	64.8	83.5	84.6	70.9	55.5	47.3	41.2
95°	40.7	47.3	53.9	79.1	127.0	190.7	215.4	188.5	144.0	110.5	87.4
97.5°	55.0	62.4	69.8	102.2	168.7	271.5	351.2	353.9	294.6	235.2	179.7
100°	68.7	76.4	84.1	113.2	180.3	299.0	434.2	513.3	501.8	433.6	358.3
102.5°	81.3	89.0	96.7	123.1	180.8	288.5	436.9	572.7	637.5	635.3	585.3
105°	93.4	101.1	108.8	134.6	183.6	274.2	407.2	553.4	667.7	729.8	737.0
107.5°	105.5	113.2	120.9	146.2	189.6	266.5	379.8	512.8	635.3	727.6	781.5
110°	117.6	125.6	133.5	157.7	197.3	264.3	361.1	474.8	590.8	689.2	759.5

TEST NUMBER: P1010034

CATALOG NUMBER: S122RDIP-B485D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	129.1	137.4	145.6	168.7	205.5	264.9	349.0	448.5	550.1	643.5	719.9
115°	141.8	149.2	156.6	180.3	213.8	267.1	340.7	427.6	518.2	602.9	674.9
117.5°	153.3	161.0	168.7	190.7	222.6	270.4	336.3	413.3	491.9	567.7	634.8
120°	164.9	172.6	180.3	201.7	231.4	273.7	332.5	402.3	473.2	541.3	599.6
122.5°	176.4	184.4	192.4	212.1	239.1	277.5	330.3	392.9	458.3	519.3	573.8
125°	187.4	195.1	202.8	222.6	247.3	281.4	327.5	384.2	444.1	500.7	549.0
127.5°	197.3	205.2	213.2	232.5	255.0	285.2	325.9	375.9	429.8	482.0	528.1
130°	206.6	214.3	222.0	241.3	262.1	289.6	324.8	367.7	416.0	463.3	506.7
132.5°	215.4	223.1	230.8	249.0	269.3	294.0	324.2	361.1	402.8	445.7	484.7
135°	223.1	230.8	238.5	256.1	275.3	297.3	323.7	355.0	390.7	427.0	463.3
137.5°	230.3	237.4	244.6	262.1	280.3	300.6	323.7	350.6	380.9	412.2	441.9
140°	236.3	243.4	250.6	267.1	284.1	302.8	323.1	346.8	371.5	397.9	423.2
142.5°	241.8	248.4	255.0	270.9	287.4	304.5	323.1	342.9	363.8	385.3	406.1
145°	247.9	253.9	259.9	274.8	290.2	305.6	322.0	339.6	356.7	374.8	391.8
147.5°	252.8	258.3	263.8	278.1	291.8	306.1	320.4	336.3	351.2	366.0	379.8
150°	257.7	262.6	267.6	280.3	292.9	305.6	318.8	331.9	345.1	357.2	368.8
152.5°	262.7	267.1	271.5	282.5	293.5	304.5	316.0	328.1	339.1	350.1	359.4
155°	267.1	271.2	275.3	284.7	294.0	303.4	312.7	323.1	333.6	342.4	350.6
157.5°	270.9	274.5	278.1	286.3	294.0	301.2	309.4	318.8	327.0	334.7	341.8
160°	274.8	277.8	280.8	287.4	294.0	299.5	306.1	313.8	321.0	327.0	333.0
162.5°	278.1	280.3	282.5	288.0	293.5	297.9	303.4	309.4	314.9	319.9	324.8
165°	280.3	282.0	283.6	288.5	292.4	295.7	299.5	304.5	308.9	312.7	316.6
167.5°	282.5	283.6	284.7	288.5	291.8	293.5	296.2	299.5	302.8	306.1	308.9
170°	283.6	284.4	285.2	288.0	290.7	291.8	293.5	295.7	298.4	300.1	302.3
172.5°	284.7	285.2	285.8	287.4	289.1	289.6	290.2	291.8	293.5	294.6	296.2
175°	285.2	285.5	285.8	286.9	288.0	287.4	288.0	288.5	290.2	290.7	291.3
177.5°	285.8	285.8	285.8	286.3	287.4	286.3	285.8	286.3	287.4	287.4	288.0
180°	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8

TEST NUMBER: P1010034

CATALOG NUMBER: S122RDIP-B485D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9
2.5°	984.5	983.1	978.8	980.2	978.1	978.1	976.7	976.7	976.7	980.2	978.1
5°	930.9	925.9	920.9	918.8	916.6	914.5	914.5	913.7	920.2	918.8	924.5
7.5°	864.4	863.0	853.0	853.0	849.4	848.0	851.5	852.3	853.0	854.4	858.0
10°	805.1	801.5	787.2	788.6	786.5	783.6	785.8	784.3	789.3	790.8	789.3
12.5°	735.0	728.6	712.8	705.0	696.4	690.0	697.8	692.1	712.1	717.8	733.6
15°	642.1	629.9	619.2	619.2	611.3	605.6	609.2	615.6	619.9	626.3	629.2
17.5°	579.9	574.8	566.3	561.3	559.1	557.0	557.0	559.8	569.1	568.4	574.1
20°	526.9	524.1	519.8	513.4	511.2	509.8	509.8	509.8	516.2	521.9	525.5
22.5°	490.5	488.3	485.5	476.9	472.6	471.2	474.7	476.9	481.9	486.2	489.8
25°	454.0	449.0	444.0	441.1	439.0	439.0	440.4	441.1	443.3	445.4	449.7
27.5°	424.0	420.4	413.3	405.4	405.4	403.3	404.7	406.1	411.1	418.3	421.8
30°	390.4	389.7	386.8	383.9	381.1	379.7	382.5	384.7	385.4	389.0	389.0
32.5°	366.1	361.1	356.1	353.2	351.8	351.1	351.8	354.6	354.6	358.9	363.9
35°	341.8	338.9	333.9	328.9	327.5	323.9	326.7	329.6	334.6	336.8	338.9
37.5°	315.3	311.7	309.6	308.2	305.3	306.0	303.9	308.2	312.4	311.7	313.2
40°	295.3	288.9	282.4	281.7	281.0	280.3	280.3	281.0	283.8	286.7	291.0
42.5°	269.5	267.4	261.7	256.0	254.5	253.1	251.7	254.5	260.3	265.3	267.4
45°	243.1	240.2	238.8	234.5	231.7	230.9	229.5	233.1	238.1	240.2	241.7
47.5°	218.8	218.1	213.8	214.5	212.4	213.1	212.4	214.5	214.5	216.6	218.1
50°	202.3	200.2	198.1	196.6	194.5	194.5	193.8	194.5	197.3	200.2	199.5
52.5°	185.9	182.3	181.6	180.9	179.5	180.9	178.7	179.5	182.3	183.8	183.0
55°	166.6	165.9	164.4	163.0	162.3	161.6	161.6	161.6	164.4	166.6	167.3
57.5°	151.6	148.0	145.1	145.1	142.3	141.6	143.0	143.7	145.9	147.3	148.7
60°	130.8	129.4	125.1	123.0	118.7	118.0	118.0	120.8	124.4	129.4	130.8
62.5°	108.7	106.5	105.8	105.8	105.8	105.8	105.8	105.8	105.8	106.5	106.5
65°	96.5	97.2	96.5	95.8	96.5	96.5	95.8	95.8	95.8	96.5	97.2
67.5°	86.5	85.8	86.5	85.8	85.1	85.1	84.4	85.1	85.8	86.5	86.5
70°	75.1	75.1	74.4	75.1	74.4	73.6	72.9	72.9	74.4	75.1	75.1
72.5°	64.3	64.3	63.6	63.6	62.2	62.2	62.9	62.2	62.2	64.3	64.3
75°	53.6	52.9	52.2	52.2	51.5	51.5	51.5	50.8	52.2	52.2	52.9
77.5°	42.2	42.2	42.2	41.5	41.5	40.8	40.8	41.5	41.5	41.5	42.2
80°	32.2	32.2	32.2	31.5	30.7	30.7	30.7	30.7	30.7	31.5	30.7
82.5°	22.2	22.2	22.2	22.2	22.2	21.4	21.4	21.4	22.2	22.2	21.4
85°	13.6	12.9	13.6	13.6	12.9	13.6	12.9	12.9	12.2	12.2	12.9
87.5°	5.7	5.0	4.3	4.3	5.0	4.3	4.3	4.3	5.0	4.3	4.3
90°	17.8	18.1	18.1	18.1	18.1	18.1	18.1	18.1	18.1	18.1	17.8
92.5°	39.0	36.8	36.3	34.1	34.6	33.5	34.6	34.1	36.3	36.8	39.0
95°	81.4	75.3	68.1	63.8	62.1	62.7	62.1	63.8	68.1	75.3	81.4
97.5°	163.2	146.7	125.3	114.3	108.3	105.0	108.3	114.3	125.3	146.7	163.2
100°	325.0	291.8	246.2	222.6	206.6	196.7	206.6	222.6	246.2	291.8	325.0
102.5°	549.6	513.9	463.3	418.8	397.9	383.6	397.9	418.8	463.3	513.9	549.6
105°	727.9	718.8	684.8	650.7	627.1	619.4	627.1	650.7	684.8	718.8	727.9
107.5°	792.5	803.5	802.9	798.0	790.8	778.2	790.8	798.0	802.9	803.5	792.5
110°	782.0	804.6	828.2	838.6	843.6	843.0	843.6	838.6	828.2	804.6	782.0

TEST NUMBER: P1010034

CATALOG NUMBER: S122RDIP-B485D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	746.6	773.2	808.4	827.7	838.1	841.9	838.1	827.7	808.4	773.2	746.6
115°	703.2	731.5	770.5	795.8	810.1	815.0	810.1	795.8	770.5	731.5	703.2
117.5°	661.7	688.6	728.7	755.7	770.5	774.3	770.5	755.7	728.7	688.6	661.7
120°	624.6	649.6	688.1	713.9	729.8	735.3	729.8	713.9	688.1	649.6	624.6
122.5°	595.8	617.7	651.2	676.5	690.3	694.7	690.3	676.5	651.2	617.7	595.8
125°	569.6	590.2	622.1	643.0	656.7	661.1	656.7	643.0	622.1	590.2	569.6
127.5°	547.4	566.6	594.6	614.4	626.5	629.8	626.5	614.4	594.6	566.6	547.4
130°	524.8	543.0	569.9	588.6	599.6	604.0	599.6	588.6	569.9	543.0	524.8
132.5°	501.4	518.2	544.6	563.3	573.2	577.1	573.2	563.3	544.6	518.2	501.4
135°	478.7	494.1	517.7	535.8	545.7	547.9	545.7	535.8	517.7	494.1	478.7
137.5°	455.6	469.3	491.9	507.8	516.6	519.9	516.6	507.8	491.9	469.3	455.6
140°	435.3	447.4	464.9	479.2	487.5	490.8	487.5	479.2	464.9	447.4	435.3
142.5°	415.8	425.4	441.9	454.5	461.6	461.6	461.6	454.5	441.9	425.4	415.8
145°	399.8	407.8	421.0	430.3	435.8	437.5	435.8	430.3	421.0	407.8	399.8
147.5°	385.8	391.8	403.4	411.1	414.9	416.0	414.9	411.1	403.4	391.8	385.8
150°	373.8	378.7	386.9	393.5	396.8	397.3	396.8	393.5	386.9	378.7	373.8
152.5°	363.5	367.7	373.7	379.2	381.4	381.4	381.4	379.2	373.7	367.7	363.5
155°	353.6	356.7	362.7	366.6	368.8	367.7	368.8	366.6	362.7	356.7	353.6
157.5°	344.3	346.8	351.2	354.5	355.6	355.6	355.6	354.5	351.2	346.8	344.3
160°	335.0	336.9	340.7	343.5	344.0	344.0	344.0	343.5	340.7	336.9	335.0
162.5°	326.2	327.5	331.4	333.0	333.6	333.0	333.6	333.0	331.4	327.5	326.2
165°	317.7	318.8	321.0	323.1	323.1	322.6	323.1	323.1	321.0	318.8	317.7
167.5°	310.0	311.1	312.2	313.3	313.3	312.7	313.3	313.3	312.2	311.1	310.0
170°	302.8	303.4	303.9	305.6	305.0	303.9	305.0	305.6	303.9	303.4	302.8
172.5°	296.5	296.8	297.3	297.9	297.3	296.8	297.3	297.9	297.3	296.8	296.5
175°	291.6	291.8	291.8	292.4	291.8	290.7	291.8	292.4	291.8	291.8	291.6
177.5°	288.0	288.0	288.0	288.0	287.4	286.3	287.4	288.0	288.0	288.0	288.0
180°	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8

TEST NUMBER: P1010034

CATALOG NUMBER: S122RDIP-B485D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9
2.5°	980.2	983.8	982.4	974.5	982.4	984.5	988.8	993.1	996.0	1000.3	1003.8
5°	918.8	925.9	930.2	925.9	940.2	942.3	952.4	958.1	966.7	973.8	979.5
7.5°	860.8	866.6	875.1	876.6	885.1	895.2	909.5	923.8	937.3	944.5	950.9
10°	798.6	808.6	821.5	818.7	831.5	847.3	862.3	885.1	896.6	909.5	920.9
12.5°	736.4	742.9	760.0	765.7	784.3	796.5	817.2	831.5	860.1	875.1	885.1
15°	627.8	654.2	675.7	701.4	725.7	748.6	767.2	792.9	817.9	829.4	845.8
17.5°	578.4	590.6	603.4	616.3	647.8	688.5	721.4	749.3	770.8	785.8	805.1
20°	526.9	539.1	553.4	565.6	584.9	614.2	654.9	702.8	728.6	744.3	762.9
22.5°	490.5	501.9	511.2	521.9	537.0	558.4	589.1	648.5	682.8	702.1	718.6
25°	451.2	465.5	475.5	483.3	495.5	519.1	544.1	577.7	639.2	654.2	677.1
27.5°	424.0	428.3	439.7	451.9	464.0	476.9	502.6	531.2	572.7	605.6	633.5
30°	391.8	402.5	413.3	418.3	429.0	447.6	463.3	494.1	526.2	552.0	585.6
32.5°	367.5	373.9	381.1	393.2	403.3	416.1	431.9	457.6	484.8	501.2	526.9
35°	340.3	344.6	359.6	364.6	374.7	387.5	403.3	423.3	452.6	465.5	484.0
37.5°	314.6	324.6	328.9	340.3	349.6	362.5	373.9	396.8	416.1	431.1	448.3
40°	294.6	298.9	306.7	316.7	324.6	334.6	348.9	365.4	386.1	398.2	413.3
42.5°	270.3	273.8	283.8	289.6	302.4	311.7	320.3	340.3	358.9	368.2	383.2
45°	243.8	252.4	258.8	270.3	277.4	288.9	299.6	313.9	331.0	341.8	350.3
47.5°	220.9	229.5	235.9	246.7	258.1	263.1	274.6	289.6	305.3	313.9	326.0
50°	202.3	205.2	217.4	222.4	234.5	244.5	252.4	265.3	282.4	287.4	297.4
52.5°	184.5	186.6	194.5	200.9	211.6	220.2	230.2	242.4	256.7	264.5	272.4
55°	168.7	170.2	173.7	180.9	188.0	198.8	208.1	219.5	231.7	240.2	247.4
57.5°	150.9	153.7	156.6	160.9	168.0	178.0	188.0	198.8	208.8	214.5	223.8
60°	130.1	134.4	139.4	144.4	149.4	156.6	168.0	178.0	187.3	192.3	199.5
62.5°	108.0	116.5	120.8	126.6	130.8	137.3	145.9	157.3	163.7	170.2	175.9
65°	97.2	98.0	98.7	104.4	112.3	118.7	126.6	135.1	145.1	149.4	153.7
67.5°	86.5	87.2	88.7	89.4	92.2	99.4	108.0	117.3	125.1	128.0	132.3
70°	75.8	75.8	78.6	79.4	80.1	80.8	87.9	97.2	104.4	108.0	113.0
72.5°	64.3	65.1	66.5	67.2	68.6	70.1	72.2	77.2	85.8	89.4	95.1
75°	52.9	53.6	54.3	55.1	57.2	57.9	60.1	62.9	66.5	70.8	74.4
77.5°	42.2	42.2	42.9	44.3	45.8	46.5	48.6	50.0	51.5	53.6	56.5
80°	31.5	32.2	32.2	33.6	33.6	34.3	35.0	37.2	38.6	40.0	41.5
82.5°	21.4	22.9	22.9	22.9	23.6	24.3	25.0	25.0	26.5	27.2	29.3
85°	12.9	13.6	13.6	13.6	12.9	14.3	14.3	15.0	15.0	15.0	15.7
87.5°	5.0	4.3	5.0	5.0	5.0	5.7	5.0	5.0	5.7	6.4	6.4
90°	17.6	16.5	17.6	18.1	18.7	18.1	14.8	11.0	8.2	7.4	6.6
92.5°	41.2	47.3	55.5	70.9	84.6	83.5	64.8	44.0	29.1	26.1	23.1
95°	87.4	110.5	144.0	188.5	215.4	190.7	127.0	79.1	53.9	47.3	40.7
97.5°	179.7	235.2	294.6	353.9	351.2	271.5	168.7	102.2	69.8	62.4	55.0
100°	358.3	433.6	501.8	513.3	434.2	299.0	180.3	113.2	84.1	76.4	68.7
102.5°	585.3	635.3	637.5	572.7	436.9	288.5	180.8	123.1	96.7	89.0	81.3
105°	737.0	729.8	667.7	553.4	407.2	274.2	183.6	134.6	108.8	101.1	93.4
107.5°	781.5	727.6	635.3	512.8	379.8	266.5	189.6	146.2	120.9	113.2	105.5
110°	759.5	689.2	590.8	474.8	361.1	264.3	197.3	157.7	133.5	125.6	117.6

TEST NUMBER: P1010034

CATALOG NUMBER: S122RDIP-B485D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	719.9	643.5	550.1	448.5	349.0	264.9	205.5	168.7	145.6	137.4	129.1
115°	674.9	602.9	518.2	427.6	340.7	267.1	213.8	180.3	156.6	149.2	141.8
117.5°	634.8	567.7	491.9	413.3	336.3	270.4	222.6	190.7	168.7	161.0	153.3
120°	599.6	541.3	473.2	402.3	332.5	273.7	231.4	201.7	180.3	172.6	164.9
122.5°	573.8	519.3	458.3	392.9	330.3	277.5	239.1	212.1	192.4	184.4	176.4
125°	549.0	500.7	444.1	384.2	327.5	281.4	247.3	222.6	202.8	195.1	187.4
127.5°	528.1	482.0	429.8	375.9	325.9	285.2	255.0	232.5	213.2	205.2	197.3
130°	506.7	463.3	416.0	367.7	324.8	289.6	262.1	241.3	222.0	214.3	206.6
132.5°	484.7	445.7	402.8	361.1	324.2	294.0	269.3	249.0	230.8	223.1	215.4
135°	463.3	427.0	390.7	355.0	323.7	297.3	275.3	256.1	238.5	230.8	223.1
137.5°	441.9	412.2	380.9	350.6	323.7	300.6	280.3	262.1	244.6	237.4	230.3
140°	423.2	397.9	371.5	346.8	323.1	302.8	284.1	267.1	250.6	243.4	236.3
142.5°	406.1	385.3	363.8	342.9	323.1	304.5	287.4	270.9	255.0	248.4	241.8
145°	391.8	374.8	356.7	339.6	322.0	305.6	290.2	274.8	259.9	253.9	247.9
147.5°	379.8	366.0	351.2	336.3	320.4	306.1	291.8	278.1	263.8	258.3	252.8
150°	368.8	357.2	345.1	331.9	318.8	305.6	292.9	280.3	267.6	262.6	257.7
152.5°	359.4	350.1	339.1	328.1	316.0	304.5	293.5	282.5	271.5	267.1	262.7
155°	350.6	342.4	333.6	323.1	312.7	303.4	294.0	284.7	275.3	271.2	267.1
157.5°	341.8	334.7	327.0	318.8	309.4	301.2	294.0	286.3	278.1	274.5	270.9
160°	333.0	327.0	321.0	313.8	306.1	299.5	294.0	287.4	280.8	277.8	274.8
162.5°	324.8	319.9	314.9	309.4	303.4	297.9	293.5	288.0	282.5	280.3	278.1
165°	316.6	312.7	308.9	304.5	299.5	295.7	292.4	288.5	283.6	282.0	280.3
167.5°	308.9	306.1	302.8	299.5	296.2	293.5	291.8	288.5	284.7	283.6	282.5
170°	302.3	300.1	298.4	295.7	293.5	291.8	290.7	288.0	285.2	284.4	283.6
172.5°	296.2	294.6	293.5	291.8	290.2	289.6	289.1	287.4	285.8	285.2	284.7
175°	291.3	290.7	290.2	288.5	288.0	287.4	288.0	286.9	285.8	285.5	285.2
177.5°	288.0	287.4	287.4	286.3	285.8	286.3	287.4	286.3	285.8	285.8	285.8
180°	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8

TEST NUMBER: P1010034

CATALOG NUMBER: S122RDIP-B485D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1028.9	1028.9	1028.9	1028.9
2.5°	1010.3	1008.1	1021.0	1035.3
5°	989.5	993.1	1009.6	1029.6
7.5°	968.1	976.0	995.3	1021.7
10°	938.1	952.4	981.7	1008.8
12.5°	908.7	928.0	955.9	988.1
15°	875.9	897.3	931.6	970.2
17.5°	839.4	863.7	903.7	945.9
20°	800.8	833.0	875.1	920.9
22.5°	757.9	796.5	840.1	890.9
25°	716.4	758.6	802.2	860.8
27.5°	675.7	717.1	765.7	825.1
30°	634.9	672.8	725.0	788.6
32.5°	591.3	630.6	685.7	750.7
35°	551.3	590.6	642.1	706.4
37.5°	508.4	550.5	599.9	666.4
40°	458.3	507.6	555.5	619.2
42.5°	416.8	469.0	515.5	575.6
45°	383.9	433.3	471.9	530.5
47.5°	353.2	393.2	432.6	486.9
50°	323.9	354.6	395.4	444.0
52.5°	293.9	320.3	355.3	401.1
55°	266.7	291.7	323.2	358.2
57.5°	241.7	259.5	291.0	322.5
60°	213.8	232.4	256.7	283.1
62.5°	190.2	204.5	227.4	249.5
65°	165.2	178.7	195.9	216.6
67.5°	142.3	154.4	168.0	184.5
70°	121.5	130.8	140.9	155.2
72.5°	99.4	109.4	118.7	130.1
75°	81.5	85.8	93.7	101.5
77.5°	62.9	68.6	72.9	79.4
80°	45.0	50.0	51.5	56.5
82.5°	30.0	32.9	35.7	37.2
85°	17.2	18.6	21.4	22.2
87.5°	6.4	7.1	8.6	10.0
90°	5.5	4.4	2.2	0.5
92.5°	18.7	15.9	11.5	8.2
95°	31.9	26.9	21.4	19.2
97.5°	45.1	37.9	31.9	28.6
100°	57.7	48.9	44.0	42.3
102.5°	69.8	61.0	56.1	55.0
105°	81.3	73.1	69.2	67.0
107.5°	93.4	85.7	81.9	80.2
110°	106.1	98.9	95.6	93.4

TEST NUMBER: P1010034

CATALOG NUMBER: S122RDIP-B485D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	118.2	111.6	107.7	105.5
115°	130.8	124.2	120.9	118.2
117.5°	142.9	136.8	133.5	131.3
120°	153.9	148.9	145.6	143.4
122.5°	165.4	159.9	156.6	155.0
125°	176.4	169.8	166.5	164.9
127.5°	186.9	179.7	175.3	173.1
130°	195.6	188.0	182.5	180.3
132.5°	203.9	195.6	189.6	186.9
135°	210.5	202.2	195.6	193.4
137.5°	217.6	208.8	202.2	199.5
140°	224.2	215.4	208.8	206.6
142.5°	230.3	221.5	215.4	213.8
145°	236.9	228.6	223.1	220.9
147.5°	243.5	235.8	230.3	228.6
150°	249.5	242.4	238.0	236.3
152.5°	255.0	249.0	244.6	244.0
155°	261.0	255.0	251.7	251.2
157.5°	266.0	260.5	257.7	257.2
160°	270.4	266.0	263.8	263.2
162.5°	274.2	270.9	268.7	269.3
165°	277.5	274.2	273.1	273.7
167.5°	280.3	278.1	277.0	277.5
170°	282.5	280.8	280.3	281.4
172.5°	284.1	282.5	283.0	283.6
175°	285.2	284.1	284.7	285.2
177.5°	285.8	284.7	285.2	286.3
180°	285.8	285.8	285.8	285.8

(END OF REPORT)