

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010046

Luminaire Tested: S122RDIP-B485D725UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010046
REPORT IS A COMBINATION OF REPORTS P988356 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B485D725UB30-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4617.0 lumens
Efficiency: N/A
Efficacy: 102.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010046

CATALOG NUMBER: S122RDIP-B485D725UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1010046

CATALOG NUMBER: S122RDIP-B485D725UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	96	92	89	85	87	84	81	78	69	67	65	55	54	53	42	42	41
2	88	81	76	71	80	74	69	65	61	58	55	49	47	45	38	37	35
3	81	72	65	60	73	66	60	55	55	50	47	44	41	39	34	33	31
4	74	64	57	51	68	59	52	48	49	44	41	40	37	34	31	29	27
5	68	57	50	44	62	53	46	41	44	39	35	36	33	30	29	26	24
6	63	52	44	39	58	48	41	36	40	35	31	33	29	26	26	24	22
7	59	47	39	34	53	43	37	32	37	32	28	30	26	24	24	22	20
8	54	43	35	30	50	40	33	29	33	29	25	28	24	21	22	20	18
9	51	39	32	27	46	36	30	26	31	26	23	26	22	19	21	18	16
10	48	36	29	25	44	33	27	23	29	24	20	24	20	18	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16945	16945	16945	16945
5°	16986	17998	17044	14379
10°	16798	19025	16917	11875
15°	16433	19030	16712	8920
20°	15995	15731	16343	7359
25°	15464	9830	15797	6261
30°	14786	6293	15187	5389
35°	13959	4837	14411	4612
40°	13038	4066	13597	4034
45°	12056	3460	12560	3387
50°	11048	2940	11565	2930
55°	9931	2556	10467	2521
60°	8940	1948	9413	1924
65°	8013	1466	8489	1663
70°	6990	1171	7540	1355
75°	5907	898	6450	1026
80°	4694	610	5046	673
85°	3263	315	3574	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 15501 cd/sqm

TEST NUMBER: P1010046

CATALOG NUMBER: S122RDIP-B485D725UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.5	2.2
10°-20°	283.4	6.1
20°-30°	364.8	7.9
30°-40°	346.1	7.5
40°-50°	296.6	6.4
50°-60°	225.9	4.9
60°-70°	142.4	3.1
70°-80°	71.1	1.5
80°-90°	20.8	0.5
90°-100°	154.7	3.4
100°-110°	545.0	11.8
110°-120°	572.3	12.4
120°-130°	470.9	10.2
130°-140°	378.3	8.2
140°-150°	285.7	6.2
150°-160°	200.9	4.4
160°-170°	118.2	2.6
170°-180°	38.5	0.8
0°-30°	749.7	16.2
0°-40°	1095.8	23.7
0°-60°	1618.2	35.0
0°-90°	1852.6	40.1
90°-120°	1272.1	27.6
90°-150°	2406.9	52.1
90°-180°	2764.0	59.9
0°-180°	4617.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1070	1070	1070	1070	1070	
5°	1071	1191	1075	952	1071	102
15°	1010	1344	1027	630	1010	284
25°	896	717	915	457	896	411
35°	735	353	759	337	735	460
45°	552	246	575	240	552	426
55°	373	170	393	168	373	336
65°	225	88	239	100	225	224
75°	106	47	115	54	106	114
85°	23	13	25	14	23	26
90°	1	25	1	25	1	3
95°	27	87	27	87	27	28
105°	93	860	93	860	93	99
115°	164	1132	164	1132	164	163
125°	229	918	229	918	229	204
135°	269	761	269	761	269	208
145°	307	608	307	608	307	193
155°	349	511	349	511	349	161
165°	380	448	380	448	380	107
175°	396	404	396	404	396	38
180°	397	397	397	397	397	

TEST NUMBER: P1010046

CATALOG NUMBER: S122RDIP-B485D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1077.2	1081.7	1083.9	1086.9	1093.6	1098.1	1104.7	1106.2	1105.5	1108.5	1100.3
5°	1071.3	1080.9	1089.9	1097.3	1109.2	1116.6	1124.8	1134.5	1136.7	1147.9	1141.2
7.5°	1063.1	1077.2	1089.9	1104.7	1122.6	1132.3	1144.9	1159.8	1166.5	1179.9	1183.6
10°	1049.7	1069.8	1091.4	1107.0	1131.5	1148.6	1160.5	1184.3	1200.0	1220.1	1217.1
12.5°	1028.1	1054.2	1083.2	1109.2	1141.2	1152.4	1174.7	1199.2	1219.3	1237.9	1254.3
15°	1009.5	1039.3	1071.3	1103.3	1139.7	1160.5	1182.9	1214.8	1236.4	1269.2	1283.3
17.5°	984.2	1022.2	1060.1	1095.8	1139.0	1162.8	1190.3	1221.5	1253.5	1284.8	1295.9
20°	958.2	999.1	1040.0	1088.4	1137.5	1160.5	1188.8	1227.5	1258.7	1283.3	1283.3
22.5°	926.9	976.8	1023.7	1069.8	1123.3	1156.8	1185.8	1231.2	1253.5	1258.7	1238.7
25°	895.7	945.5	996.9	1054.2	1115.2	1144.9	1177.7	1220.1	1227.5	1206.7	1154.6
27.5°	858.5	914.3	972.3	1034.1	1098.1	1135.2	1165.0	1193.3	1179.1	1123.3	1042.3
30°	820.6	880.8	946.3	1005.1	1082.4	1116.6	1141.9	1150.1	1105.5	1014.7	909.8
32.5°	781.1	839.9	909.1	979.8	1057.9	1090.6	1107.0	1085.4	1003.6	889.0	761.0
35°	735.0	801.2	873.4	947.0	1024.4	1049.0	1058.6	1005.8	900.9	752.9	625.7
37.5°	693.3	759.6	836.9	912.1	987.2	1000.6	990.9	908.3	775.2	628.6	504.4
40°	644.2	714.9	790.8	874.9	936.6	940.3	916.5	809.4	644.2	506.6	430.0
42.5°	598.9	670.3	746.2	831.7	878.6	865.9	834.0	693.3	537.9	436.7	374.9
45°	552.0	619.7	701.5	777.4	810.9	781.1	732.8	583.2	451.6	375.7	328.1
47.5°	506.6	569.9	650.9	723.9	729.8	696.3	639.0	488.8	391.3	330.3	291.6
50°	462.0	525.2	601.1	661.4	655.4	609.3	544.6	424.8	340.0	291.6	259.6
52.5°	417.3	474.6	548.3	595.9	570.6	526.0	462.0	360.1	296.8	254.4	229.9
55°	372.7	426.3	489.5	528.9	488.8	437.4	392.1	308.7	257.4	223.2	204.6
57.5°	335.5	377.9	435.9	459.8	411.4	371.2	331.8	265.6	223.2	198.6	177.1
60°	294.6	333.3	380.9	395.0	345.2	312.5	279.0	224.7	191.2	169.6	155.5
62.5°	259.6	291.6	328.1	328.1	284.2	259.6	234.3	188.2	160.7	143.6	136.9
65°	225.4	248.5	274.5	271.5	234.3	212.8	192.7	155.5	134.7	122.7	116.1
67.5°	191.9	209.8	226.9	216.5	189.7	171.1	152.5	125.7	111.6	103.4	94.5
70°	161.4	175.6	184.5	174.8	148.0	132.4	119.0	101.2	90.0	79.6	74.4
72.5°	135.4	141.3	144.3	132.4	110.1	101.2	91.5	78.9	69.2	64.0	62.5
75°	105.6	110.8	108.6	99.7	81.1	74.4	67.0	58.0	55.8	52.8	51.3
77.5°	82.6	82.6	78.9	70.7	58.0	52.8	49.8	45.4	43.1	42.4	40.9
80°	58.8	58.0	55.8	46.9	39.4	36.5	36.5	33.5	32.7	31.2	31.2
82.5°	38.7	38.7	35.7	28.3	26.0	25.3	24.5	23.1	23.1	22.3	22.3
85°	23.1	21.6	17.9	15.6	14.9	14.9	14.1	13.4	14.1	13.4	13.4
87.5°	10.4	8.2	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
90°	0.8	3.1	6.1	7.6	9.2	10.4	11.5	15.3	20.6	25.2	26.0
92.5°	11.5	16.0	22.1	26.0	32.1	36.3	40.5	61.1	90.1	116.0	117.6
95°	26.7	29.8	37.4	44.3	56.5	65.6	74.8	109.9	176.3	264.9	299.2
97.5°	39.7	44.3	52.7	62.6	76.3	86.6	97.0	142.0	234.4	377.1	487.8
100°	58.8	61.1	67.9	80.2	95.4	106.1	116.8	157.3	250.4	415.3	603.1
102.5°	76.3	77.9	84.7	97.0	113.0	123.7	134.4	171.0	251.2	400.8	606.9
105°	93.1	96.2	101.5	113.0	129.8	140.5	151.2	187.0	255.0	380.9	565.7
107.5°	111.5	113.7	119.1	129.8	146.6	157.2	167.9	203.1	263.4	370.2	527.5
110°	129.8	132.8	137.4	147.3	163.4	174.4	185.5	219.1	274.1	367.2	501.5

TEST NUMBER: P1010046

CATALOG NUMBER: S122RDIP-B485D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	146.6	149.6	155.0	164.1	179.4	190.9	202.3	234.4	285.5	368.0	484.8
115°	164.1	167.9	172.5	181.7	197.0	207.3	217.6	250.4	297.0	371.0	473.3
117.5°	182.4	185.5	190.1	198.5	213.0	223.7	234.4	264.9	309.2	375.6	467.2
120°	199.2	202.3	206.9	213.7	229.0	239.7	250.4	280.2	321.4	380.2	461.8
122.5°	215.3	217.6	222.1	229.8	245.0	256.1	267.2	294.7	332.1	385.5	458.8
125°	229.0	231.3	235.9	245.0	260.3	271.0	281.7	309.2	343.5	390.9	455.0
127.5°	240.5	243.5	249.6	259.6	274.1	285.2	296.2	322.9	354.2	396.2	452.7
130°	250.4	253.4	261.1	271.8	287.0	297.7	308.4	335.1	364.1	402.3	451.2
132.5°	259.6	263.4	271.8	283.2	299.2	309.9	320.6	345.8	374.1	408.4	450.4
135°	268.7	271.8	280.9	292.4	309.9	320.6	331.3	355.7	382.5	413.0	449.6
137.5°	277.1	280.9	290.1	302.3	319.9	329.8	339.7	364.1	389.3	417.6	449.6
140°	287.0	290.1	299.2	311.5	328.3	338.2	348.1	371.0	394.7	420.6	448.9
142.5°	297.0	299.2	307.6	319.9	335.9	345.0	354.2	376.3	399.3	422.9	448.9
145°	306.9	309.9	317.6	329.0	344.3	352.7	361.1	381.7	403.1	424.4	447.3
147.5°	317.6	319.9	327.5	338.2	351.2	358.8	366.4	386.3	405.4	425.2	445.1
150°	328.3	330.5	336.7	346.6	358.0	364.9	371.8	389.3	406.9	424.4	442.8
152.5°	338.9	339.7	345.8	354.2	364.9	371.0	377.1	392.4	407.6	422.9	438.9
155°	348.9	349.6	354.2	362.6	371.0	376.8	382.5	395.4	408.4	421.4	434.4
157.5°	357.3	358.0	361.8	369.5	376.3	381.3	386.3	397.7	408.4	418.3	429.8
160°	365.7	366.4	369.5	375.6	381.7	385.9	390.1	399.3	408.4	416.0	425.2
162.5°	374.1	373.3	376.3	380.9	386.3	389.4	392.4	400.0	407.6	413.8	421.4
165°	380.2	379.4	380.9	385.5	389.3	391.6	393.9	400.8	406.1	410.7	416.0
167.5°	385.5	384.7	386.3	389.3	392.4	393.9	395.4	400.8	405.4	407.6	411.5
170°	390.9	389.3	390.1	392.4	393.9	395.0	396.2	400.0	403.8	405.4	407.6
172.5°	393.9	393.1	392.4	394.7	395.4	396.2	397.0	399.3	401.5	402.3	403.1
175°	396.2	395.4	394.7	396.2	396.2	396.6	397.0	398.5	400.0	399.3	400.0
177.5°	397.7	396.2	395.4	397.0	397.0	397.0	397.0	397.7	399.3	397.7	397.0
180°	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0

TEST NUMBER: P1010046

CATALOG NUMBER: S122RDIP-B485D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1108.5	1110.0	1112.2	1122.6	1124.1	1127.1	1125.6	1125.6	1126.3	1124.8	1125.6
5°	1156.1	1158.3	1169.5	1182.1	1185.1	1182.1	1185.8	1191.0	1191.0	1191.0	1189.6
7.5°	1200.7	1208.9	1221.5	1240.1	1243.9	1247.6	1254.3	1249.8	1251.3	1258.0	1255.8
10°	1243.9	1255.8	1269.9	1285.5	1293.7	1298.9	1301.9	1308.6	1324.2	1306.4	1313.0
12.5°	1284.8	1301.9	1316.8	1333.9	1339.8	1346.5	1348.8	1354.7	1354.7	1354.0	1359.2
15°	1311.6	1327.2	1340.6	1351.7	1353.2	1351.7	1350.2	1351.0	1353.2	1344.3	1349.5
17.5°	1317.5	1319.0	1323.5	1319.0	1319.7	1304.1	1295.2	1293.0	1272.1	1272.9	1290.0
20°	1288.5	1263.2	1256.5	1232.0	1217.1	1176.9	1175.4	1164.3	1120.4	1133.8	1130.8
22.5°	1208.9	1165.7	1108.5	1080.2	1066.1	1023.7	990.9	967.9	952.2	936.6	929.9
25°	1104.0	1034.1	953.0	897.2	889.0	849.6	789.3	761.0	727.6	717.2	735.0
27.5°	968.6	877.8	786.3	700.8	685.2	649.5	619.0	598.9	560.2	558.0	559.4
30°	784.9	693.3	616.7	560.9	522.2	505.9	485.8	470.9	455.3	461.2	462.7
32.5°	645.0	558.0	486.5	456.8	438.9	428.5	411.4	401.7	395.0	392.8	392.1
35°	512.6	454.5	422.6	393.5	383.1	375.7	363.0	358.6	352.6	353.4	353.4
37.5°	438.9	390.6	366.8	351.9	342.2	338.5	330.3	325.8	322.1	320.6	322.9
40°	378.7	345.2	330.3	316.9	308.7	307.2	302.8	297.6	293.1	293.9	296.1
42.5°	334.8	315.4	297.6	287.2	281.2	279.0	275.3	271.5	271.5	269.3	268.6
45°	299.8	284.2	269.3	259.6	255.9	252.9	248.5	247.7	244.8	245.5	246.2
47.5°	268.6	255.9	244.8	235.1	231.4	230.6	226.2	223.2	223.2	222.4	221.7
50°	240.3	227.6	218.0	212.8	207.6	206.1	205.3	204.6	203.1	203.1	203.8
52.5°	217.2	204.6	197.1	192.7	189.7	188.2	188.2	187.5	187.5	187.5	186.7
55°	191.9	181.5	175.6	174.1	172.6	171.8	171.1	169.6	168.9	170.4	168.9
57.5°	168.1	164.4	159.2	157.7	154.0	154.0	151.8	150.3	148.8	150.3	150.3
60°	149.5	144.3	141.3	136.9	133.9	130.9	127.2	126.5	125.0	124.2	123.5
62.5°	130.2	125.7	118.3	111.6	107.1	104.2	102.7	101.9	101.9	101.2	101.2
65°	108.6	98.2	94.5	92.2	91.5	90.8	89.3	88.5	89.3	88.5	89.3
67.5°	84.8	83.3	81.1	79.6	78.9	78.1	78.1	77.4	77.4	77.4	77.4
70°	73.6	69.9	69.2	67.7	67.7	67.0	67.0	67.0	67.0	66.2	67.7
72.5°	61.0	58.8	58.0	57.3	57.3	57.3	56.5	56.5	56.5	55.8	56.5
75°	49.8	49.1	47.6	47.6	46.9	47.6	46.9	46.9	46.1	46.9	46.9
77.5°	40.2	39.4	38.7	38.7	37.9	37.9	37.9	37.9	37.9	37.9	38.7
80°	30.5	29.8	29.0	29.8	29.0	29.8	29.0	29.0	29.8	29.0	29.0
82.5°	22.3	21.6	21.6	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8
85°	13.4	12.6	12.6	13.4	12.6	13.4	12.6	12.6	12.6	13.4	13.4
87.5°	6.0	6.7	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.7
90°	25.2	24.4	22.9	24.4	24.8	25.2	25.2	25.2	25.2	25.2	25.2
92.5°	98.5	77.1	65.7	57.3	54.2	51.1	50.4	47.3	48.1	46.6	48.1
95°	261.8	200.0	153.4	121.4	113.0	104.6	94.7	88.6	86.3	87.0	86.3
97.5°	491.6	409.2	326.7	249.6	226.7	203.8	174.1	158.8	150.4	145.8	150.4
100°	713.0	697.0	602.3	497.7	451.6	405.4	342.0	309.2	287.0	273.3	287.0
102.5°	795.4	885.5	882.5	813.0	763.4	713.8	643.5	581.7	552.7	532.8	552.7
105°	768.7	927.5	1013.8	1023.7	1011.1	998.5	951.2	903.9	871.0	860.3	871.0
107.5°	712.2	882.5	1010.7	1085.5	1100.8	1116.1	1115.3	1108.4	1098.5	1081.0	1098.5
110°	659.6	820.6	957.3	1055.0	1086.3	1117.6	1150.4	1164.9	1171.8	1171.0	1171.8

TEST NUMBER: P1010046

CATALOG NUMBER: S122RDIP-B485D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	622.9	764.2	893.9	1000.0	1037.0	1074.1	1122.9	1149.7	1164.2	1169.5	1164.2
115°	593.9	719.9	837.4	937.4	976.8	1016.1	1070.3	1105.4	1125.2	1132.1	1125.2
117.5°	574.1	683.2	788.6	881.7	919.1	956.5	1012.3	1049.7	1070.3	1075.6	1070.3
120°	558.8	657.3	751.9	832.9	867.6	902.3	955.8	991.6	1013.8	1021.4	1013.8
122.5°	545.8	636.7	721.4	797.0	827.5	858.0	904.6	939.7	958.8	964.9	958.8
125°	533.6	616.8	695.4	762.6	791.2	819.9	864.2	893.2	912.2	918.4	912.2
127.5°	522.2	597.0	669.5	733.6	760.4	787.1	826.0	853.5	870.3	874.8	870.3
130°	510.7	577.9	643.5	703.8	729.0	754.2	791.6	817.6	832.9	839.0	832.9
132.5°	501.5	559.6	619.1	673.3	696.6	719.9	756.5	782.5	796.2	801.6	796.2
135°	493.1	542.8	593.2	643.5	664.9	686.3	719.1	744.3	758.0	761.1	758.0
137.5°	487.0	529.0	572.5	613.8	632.8	651.9	683.2	705.4	717.6	722.2	717.6
140°	481.7	516.0	552.7	587.8	604.6	621.4	645.8	665.7	677.1	681.7	677.1
142.5°	476.4	505.4	535.1	564.1	577.5	590.9	613.8	631.3	641.2	641.2	641.2
145°	471.8	495.4	520.6	544.3	555.3	566.4	584.8	597.7	605.4	607.7	605.4
147.5°	467.2	487.8	508.4	527.5	535.9	544.3	560.3	571.0	576.4	577.9	576.4
150°	461.1	479.4	496.2	512.2	519.1	526.0	537.4	546.6	551.2	551.9	551.2
152.5°	455.7	471.0	486.3	499.3	505.0	510.7	519.1	526.7	529.8	529.8	529.8
155°	448.9	463.4	475.6	487.0	491.2	495.4	503.8	509.2	512.2	510.7	512.2
157.5°	442.8	454.2	464.9	474.8	478.2	481.7	487.8	492.4	493.9	493.9	493.9
160°	435.9	445.8	454.2	462.6	465.3	468.0	473.3	477.1	477.9	477.9	477.9
162.5°	429.8	437.4	444.3	451.2	453.1	455.0	460.3	462.6	463.4	462.6	463.4
165°	422.9	429.0	434.4	439.7	441.2	442.8	445.8	448.9	448.9	448.1	448.9
167.5°	416.0	420.6	425.2	429.0	430.6	432.1	433.6	435.1	435.1	434.4	435.1
170°	410.7	414.5	416.8	419.9	420.6	421.4	422.2	424.4	423.7	422.2	423.7
172.5°	405.4	407.6	409.2	411.5	411.8	412.2	413.0	413.8	413.0	412.2	413.0
175°	400.8	403.1	403.8	404.6	405.0	405.4	405.4	406.1	405.4	403.8	405.4
177.5°	397.7	399.3	399.3	400.0	400.0	400.0	400.0	400.0	399.3	397.7	399.3
180°	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0

TEST NUMBER: P1010046

CATALOG NUMBER: S122RDIP-B485D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1128.6	1123.3	1121.9	1123.3	1121.9	1122.6	1117.4	1098.1	1103.3	1095.1	1099.5
5°	1192.5	1188.1	1178.4	1176.9	1175.4	1173.9	1166.5	1149.4	1142.7	1131.5	1130.8
7.5°	1253.5	1253.5	1246.1	1240.9	1234.2	1229.0	1219.3	1194.0	1183.6	1170.2	1162.8
10°	1313.8	1294.4	1302.6	1297.4	1281.1	1278.1	1260.2	1245.4	1225.3	1211.9	1200.0
12.5°	1356.9	1351.0	1343.5	1339.1	1334.6	1325.0	1313.0	1275.1	1264.7	1237.9	1224.5
15°	1355.5	1351.7	1354.0	1354.0	1352.5	1350.2	1340.6	1313.0	1295.2	1269.2	1246.1
17.5°	1282.5	1292.2	1301.9	1308.6	1323.5	1330.2	1339.1	1322.7	1311.6	1289.2	1264.7
20°	1155.3	1179.1	1207.4	1213.4	1226.8	1266.2	1284.0	1298.2	1302.6	1295.2	1275.1
22.5°	978.3	998.4	1066.8	1065.3	1084.7	1131.5	1183.6	1226.0	1259.5	1278.1	1270.6
25°	766.3	794.5	831.0	858.5	921.7	991.7	1056.4	1124.1	1182.1	1233.4	1246.1
27.5°	579.5	616.7	645.7	682.2	714.2	796.8	880.1	985.7	1053.4	1150.9	1201.5
30°	468.7	485.8	514.8	531.9	547.5	610.8	705.3	809.4	928.4	1040.8	1127.8
32.5°	400.2	412.1	433.7	441.2	457.5	499.9	559.4	654.7	777.4	913.6	1028.1
35°	359.3	372.0	376.4	383.1	396.5	423.3	464.2	533.4	644.2	777.4	914.3
37.5°	324.4	331.1	343.7	348.2	352.6	372.7	400.2	448.6	522.2	631.6	783.4
40°	299.8	303.5	310.2	313.9	316.9	331.1	355.6	388.3	442.6	526.0	665.8
42.5°	273.8	278.2	282.7	287.2	290.9	302.0	316.9	348.2	384.6	447.8	549.0
45°	248.5	251.5	256.7	259.6	264.8	273.8	287.2	308.7	341.5	381.6	463.5
47.5°	225.4	229.1	231.4	235.1	238.8	248.5	261.1	275.3	302.0	341.5	401.0
50°	204.6	209.0	212.0	212.8	215.7	224.7	235.1	250.7	267.8	298.3	350.4
52.5°	189.7	190.4	192.7	195.7	194.9	200.1	209.8	221.7	239.5	264.1	302.0
55°	172.6	174.8	176.3	177.1	177.1	181.5	186.7	197.9	212.0	232.1	264.1
57.5°	151.0	153.3	157.7	159.2	161.4	163.7	165.9	173.3	185.2	204.6	230.6
60°	128.7	130.2	134.7	137.6	139.1	145.1	148.0	154.0	160.7	174.8	199.4
62.5°	103.4	104.9	107.1	110.1	113.1	122.0	129.4	135.4	140.6	150.3	170.4
65°	90.0	90.8	92.2	93.0	93.7	97.5	104.2	112.3	122.0	129.4	141.3
67.5°	78.1	78.9	79.6	81.1	81.8	82.6	85.6	87.8	97.5	107.9	116.8
70°	67.0	68.4	69.2	69.2	69.9	71.4	72.9	75.9	78.9	84.1	95.2
72.5°	56.5	57.3	58.8	58.8	58.8	60.3	61.7	63.2	64.7	67.7	72.2
75°	46.9	48.4	48.4	48.4	49.1	49.1	50.6	52.1	53.6	55.8	57.3
77.5°	38.7	38.7	38.7	38.7	39.4	39.4	40.2	41.7	42.4	43.1	44.6
80°	29.0	29.8	29.8	29.8	30.5	30.5	30.5	32.0	32.7	32.7	34.2
82.5°	21.6	21.6	21.6	22.3	21.6	22.3	22.3	23.1	22.3	23.1	23.8
85°	13.4	13.4	13.4	14.1	14.1	14.1	14.1	14.1	14.1	14.1	14.9
87.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	7.4	6.7	6.7
90°	25.2	25.2	25.2	24.8	24.4	22.9	24.4	25.2	26.0	25.2	20.6
92.5°	47.3	50.4	51.1	54.2	57.3	65.7	77.1	98.5	117.6	116.0	90.1
95°	88.6	94.7	104.6	113.0	121.4	153.4	200.0	261.8	299.2	264.9	176.3
97.5°	158.8	174.1	203.8	226.7	249.6	326.7	409.2	491.6	487.8	377.1	234.4
100°	309.2	342.0	405.4	451.6	497.7	602.3	697.0	713.0	603.1	415.3	250.4
102.5°	581.7	643.5	713.8	763.4	813.0	882.5	885.5	795.4	606.9	400.8	251.2
105°	903.9	951.2	998.5	1011.1	1023.7	1013.8	927.5	768.7	565.7	380.9	255.0
107.5°	1108.4	1115.3	1116.1	1100.8	1085.5	1010.7	882.5	712.2	527.5	370.2	263.4
110°	1164.9	1150.4	1117.6	1086.3	1055.0	957.3	820.6	659.6	501.5	367.2	274.1

TEST NUMBER: P1010046

CATALOG NUMBER: S122RDIP-B485D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1149.7	1122.9	1074.1	1037.0	1000.0	893.9	764.2	622.9	484.8	368.0	285.5
115°	1105.4	1070.3	1016.1	976.8	937.4	837.4	719.9	593.9	473.3	371.0	297.0
117.5°	1049.7	1012.3	956.5	919.1	881.7	788.6	683.2	574.1	467.2	375.6	309.2
120°	991.6	955.8	902.3	867.6	832.9	751.9	657.3	558.8	461.8	380.2	321.4
122.5°	939.7	904.6	858.0	827.5	797.0	721.4	636.7	545.8	458.8	385.5	332.1
125°	893.2	864.2	819.9	791.2	762.6	695.4	616.8	533.6	455.0	390.9	343.5
127.5°	853.5	826.0	787.1	760.4	733.6	669.5	597.0	522.2	452.7	396.2	354.2
130°	817.6	791.6	754.2	729.0	703.8	643.5	577.9	510.7	451.2	402.3	364.1
132.5°	782.5	756.5	719.9	696.6	673.3	619.1	559.6	501.5	450.4	408.4	374.1
135°	744.3	719.1	686.3	664.9	643.5	593.2	542.8	493.1	449.6	413.0	382.5
137.5°	705.4	683.2	651.9	632.8	613.8	572.5	529.0	487.0	449.6	417.6	389.3
140°	665.7	645.8	621.4	604.6	587.8	552.7	516.0	481.7	448.9	420.6	394.7
142.5°	631.3	613.8	590.9	577.5	564.1	535.1	505.4	476.4	448.9	422.9	399.3
145°	597.7	584.8	566.4	555.3	544.3	520.6	495.4	471.8	447.3	424.4	403.1
147.5°	571.0	560.3	544.3	535.9	527.5	508.4	487.8	467.2	445.1	425.2	405.4
150°	546.6	537.4	526.0	519.1	512.2	496.2	479.4	461.1	442.8	424.4	406.9
152.5°	526.7	519.1	510.7	505.0	499.3	486.3	471.0	455.7	438.9	422.9	407.6
155°	509.2	503.8	495.4	491.2	487.0	475.6	463.4	448.9	434.4	421.4	408.4
157.5°	492.4	487.8	481.7	478.2	474.8	464.9	454.2	442.8	429.8	418.3	408.4
160°	477.1	473.3	468.0	465.3	462.6	454.2	445.8	435.9	425.2	416.0	408.4
162.5°	462.6	460.3	455.0	453.1	451.2	444.3	437.4	429.8	421.4	413.8	407.6
165°	448.9	445.8	442.8	441.2	439.7	434.4	429.0	422.9	416.0	410.7	406.1
167.5°	435.1	433.6	432.1	430.6	429.0	425.2	420.6	416.0	411.5	407.6	405.4
170°	424.4	422.2	421.4	420.6	419.9	416.8	414.5	410.7	407.6	405.4	403.8
172.5°	413.8	413.0	412.2	411.8	411.5	409.2	407.6	405.4	403.1	402.3	401.5
175°	406.1	405.4	405.4	405.0	404.6	403.8	403.1	400.8	400.0	399.3	400.0
177.5°	400.0	400.0	400.0	400.0	400.0	399.3	399.3	397.7	397.0	397.7	399.3
180°	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0

TEST NUMBER: P1010046

CATALOG NUMBER: S122RDIP-B485D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1092.8	1089.1	1089.1	1086.9	1086.9	1075.0	1075.0	1078.7	1074.2	1069.0	1061.6
5°	1121.1	1112.9	1110.7	1107.7	1098.1	1083.2	1077.2	1075.0	1066.1	1054.9	1042.3
7.5°	1147.9	1134.5	1127.8	1121.1	1108.5	1087.6	1075.7	1067.5	1054.2	1037.0	1020.7
10°	1173.9	1156.8	1139.7	1131.5	1113.7	1087.6	1070.5	1057.1	1037.8	1014.7	991.7
12.5°	1197.7	1162.0	1159.1	1142.7	1116.6	1086.9	1060.9	1041.5	1017.0	990.2	963.4
15°	1218.6	1182.1	1164.3	1149.4	1115.2	1078.0	1050.4	1026.6	993.9	963.4	930.7
17.5°	1229.0	1189.6	1177.7	1153.1	1118.1	1069.8	1032.6	1003.6	967.9	931.4	894.2
20°	1239.4	1193.3	1173.9	1156.8	1109.2	1054.2	1012.5	979.0	939.6	896.4	855.5
22.5°	1244.6	1193.3	1170.2	1146.4	1100.3	1037.0	987.9	948.5	902.4	858.5	809.4
25°	1235.7	1188.8	1161.3	1136.7	1084.7	1016.2	959.7	915.0	865.9	816.1	766.3
27.5°	1213.4	1178.4	1146.4	1121.1	1063.1	989.4	929.9	879.3	828.7	773.0	722.4
30°	1171.7	1156.1	1130.8	1102.5	1039.3	965.6	895.0	842.9	787.1	731.3	678.5
32.5°	1107.0	1120.4	1104.0	1079.5	1011.0	932.9	857.8	804.9	743.9	683.7	635.3
35°	1028.1	1075.7	1066.8	1049.7	981.3	897.9	822.8	758.8	697.8	636.8	588.5
37.5°	941.8	1014.0	1021.4	1011.0	947.0	862.2	779.6	717.2	654.7	592.9	543.8
40°	823.5	934.4	958.2	962.7	911.3	819.1	732.8	671.8	610.0	549.8	490.3
42.5°	714.9	854.8	884.5	903.1	865.9	776.7	689.6	621.9	560.9	506.6	447.1
45°	613.0	758.8	807.2	831.0	814.6	728.3	638.3	575.1	519.3	469.4	412.1
47.5°	508.1	654.7	722.4	760.3	760.3	679.2	589.2	526.7	473.1	430.7	380.2
50°	438.2	560.2	630.1	680.0	693.3	629.4	544.6	483.6	433.0	386.8	348.2
52.5°	373.5	482.8	540.8	592.9	631.6	575.8	494.7	439.7	389.8	346.7	316.2
55°	322.9	404.7	457.5	514.8	558.0	521.5	446.4	392.8	349.7	313.9	287.9
57.5°	274.5	345.9	389.1	439.7	485.8	458.3	398.0	351.9	313.9	282.7	259.6
60°	233.6	291.6	325.1	364.5	421.8	402.5	352.6	310.2	279.7	251.5	232.1
62.5°	198.6	244.8	273.0	301.3	353.4	344.4	305.8	273.0	247.0	223.2	206.8
65°	162.9	200.9	223.2	247.7	289.4	293.1	261.9	238.8	215.0	194.2	179.3
67.5°	131.7	161.4	181.5	202.4	235.8	246.2	224.7	205.3	185.2	168.1	154.7
70°	106.4	127.2	142.1	158.5	186.0	198.6	187.5	174.1	157.7	143.6	131.7
72.5°	84.1	97.5	106.4	119.0	141.3	154.0	153.3	141.3	129.4	119.8	110.1
75°	61.7	72.2	79.6	87.8	105.6	117.5	120.5	115.3	103.4	96.0	88.5
77.5°	46.9	52.8	56.5	62.5	75.1	85.6	90.0	88.5	80.3	74.4	69.2
80°	35.7	37.2	38.7	40.9	51.3	61.0	64.0	63.2	58.8	56.5	50.6
82.5°	25.3	26.0	26.8	27.5	31.2	39.4	42.4	43.9	40.2	37.9	32.7
85°	14.9	15.6	15.6	17.1	17.9	20.1	25.3	25.3	24.5	21.6	20.8
87.5°	7.4	7.4	6.7	6.7	7.4	8.2	9.7	11.2	9.7	8.9	8.2
90°	15.3	11.5	10.4	9.2	7.6	6.1	3.1	0.8	3.1	6.1	7.6
92.5°	61.1	40.5	36.3	32.1	26.0	22.1	16.0	11.5	16.0	22.1	26.0
95°	109.9	74.8	65.6	56.5	44.3	37.4	29.8	26.7	29.8	37.4	44.3
97.5°	142.0	97.0	86.6	76.3	62.6	52.7	44.3	39.7	44.3	52.7	62.6
100°	157.3	116.8	106.1	95.4	80.2	67.9	61.1	58.8	61.1	67.9	80.2
102.5°	171.0	134.4	123.7	113.0	97.0	84.7	77.9	76.3	77.9	84.7	97.0
105°	187.0	151.2	140.5	129.8	113.0	101.5	96.2	93.1	96.2	101.5	113.0
107.5°	203.1	167.9	157.2	146.6	129.8	119.1	113.7	111.5	113.7	119.1	129.8
110°	219.1	185.5	174.4	163.4	147.3	137.4	132.8	129.8	132.8	137.4	147.3

TEST NUMBER: P1010046

CATALOG NUMBER: S122RDIP-B485D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	234.4	202.3	190.9	179.4	164.1	155.0	149.6	146.6	149.6	155.0	164.1
115°	250.4	217.6	207.3	197.0	181.7	172.5	167.9	164.1	167.9	172.5	181.7
117.5°	264.9	234.4	223.7	213.0	198.5	190.1	185.5	182.4	185.5	190.1	198.5
120°	280.2	250.4	239.7	229.0	213.7	206.9	202.3	199.2	202.3	206.9	213.7
122.5°	294.7	267.2	256.1	245.0	229.8	222.1	217.6	215.3	217.6	222.1	229.8
125°	309.2	281.7	271.0	260.3	245.0	235.9	231.3	229.0	231.3	235.9	245.0
127.5°	322.9	296.2	285.2	274.1	259.6	249.6	243.5	240.5	243.5	249.6	259.6
130°	335.1	308.4	297.7	287.0	271.8	261.1	253.4	250.4	253.4	261.1	271.8
132.5°	345.8	320.6	309.9	299.2	283.2	271.8	263.4	259.6	263.4	271.8	283.2
135°	355.7	331.3	320.6	309.9	292.4	280.9	271.8	268.7	271.8	280.9	292.4
137.5°	364.1	339.7	329.8	319.9	302.3	290.1	280.9	277.1	280.9	290.1	302.3
140°	371.0	348.1	338.2	328.3	311.5	299.2	290.1	287.0	290.1	299.2	311.5
142.5°	376.3	354.2	345.0	335.9	319.9	307.6	299.2	297.0	299.2	307.6	319.9
145°	381.7	361.1	352.7	344.3	329.0	317.6	309.9	306.9	309.9	317.6	329.0
147.5°	386.3	366.4	358.8	351.2	338.2	327.5	319.9	317.6	319.9	327.5	338.2
150°	389.3	371.8	364.9	358.0	346.6	336.7	330.5	328.3	330.5	336.7	346.6
152.5°	392.4	377.1	371.0	364.9	354.2	345.8	339.7	338.9	339.7	345.8	354.2
155°	395.4	382.5	376.8	371.0	362.6	354.2	349.6	348.9	349.6	354.2	362.6
157.5°	397.7	386.3	381.3	376.3	369.5	361.8	358.0	357.3	358.0	361.8	369.5
160°	399.3	390.1	385.9	381.7	375.6	369.5	366.4	365.7	366.4	369.5	375.6
162.5°	400.0	392.4	389.4	386.3	380.9	376.3	373.3	374.1	373.3	376.3	380.9
165°	400.8	393.9	391.6	389.3	385.5	380.9	379.4	380.2	379.4	380.9	385.5
167.5°	400.8	395.4	393.9	392.4	389.3	386.3	384.7	385.5	384.7	386.3	389.3
170°	400.0	396.2	395.0	393.9	392.4	390.1	389.3	390.9	389.3	390.1	392.4
172.5°	399.3	397.0	396.2	395.4	394.7	392.4	393.1	393.9	393.1	392.4	394.7
175°	398.5	397.0	396.6	396.2	396.2	394.7	395.4	396.2	395.4	394.7	396.2
177.5°	397.7	397.0	397.0	397.0	397.0	395.4	396.2	397.7	396.2	395.4	397.0
180°	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0

TEST NUMBER: P1010046

CATALOG NUMBER: S122RDIP-B485D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1058.6	1059.4	1061.6	1054.9	1044.5	1040.0	1026.6	1024.4	1022.2	1022.2	1024.4
5°	1034.8	1031.8	1032.6	1019.9	1005.1	996.1	977.5	980.5	970.8	964.9	966.4
7.5°	1008.8	1000.6	999.9	983.5	964.9	948.5	929.2	924.7	915.8	905.4	900.9
10°	976.0	970.1	958.9	940.3	916.5	903.1	877.1	861.5	859.2	843.6	837.7
12.5°	942.6	932.2	921.0	895.0	868.2	846.6	827.3	810.1	798.2	784.9	775.9
15°	903.9	891.2	878.6	851.1	819.8	798.2	769.2	743.9	709.0	681.4	665.8
17.5°	861.5	847.3	830.2	799.7	769.2	739.5	685.9	656.2	631.6	615.2	605.6
20°	817.6	802.0	784.9	754.4	701.5	649.5	619.7	596.6	581.8	565.4	553.5
22.5°	771.5	755.1	736.5	688.9	633.1	596.6	573.6	552.0	530.4	521.5	515.5
25°	728.3	713.4	689.6	624.9	581.0	547.5	521.5	507.4	496.2	484.3	473.1
27.5°	683.7	656.2	622.7	568.4	540.8	506.6	488.0	477.6	458.3	450.1	444.9
30°	630.1	599.6	567.6	528.9	496.9	473.1	456.0	438.9	427.8	419.6	410.7
32.5°	575.8	546.8	526.7	486.5	462.7	438.2	421.8	411.4	395.0	389.8	386.1
35°	528.9	504.4	486.5	453.8	431.5	409.2	397.3	381.6	371.2	361.6	355.6
37.5°	482.8	469.4	450.8	423.3	399.5	381.6	365.3	360.1	345.9	340.7	334.8
40°	450.8	430.7	415.1	391.3	371.2	351.9	341.5	329.6	319.9	311.7	309.5
42.5°	412.1	397.3	388.3	362.3	341.5	330.3	317.7	304.3	296.8	290.1	282.0
45°	383.1	369.7	357.1	336.3	317.7	303.5	292.4	283.4	270.8	267.8	255.2
47.5°	352.6	339.2	329.6	308.7	291.6	278.2	270.0	258.1	247.7	241.0	235.1
50°	322.1	311.0	302.0	284.2	269.3	255.2	244.0	232.1	227.6	216.5	212.8
52.5°	293.1	285.7	276.0	258.9	244.0	232.1	220.2	210.5	203.8	197.9	193.4
55°	268.6	256.7	252.2	233.6	220.9	208.3	197.9	191.9	183.8	180.0	176.3
57.5°	241.0	234.3	226.9	212.8	198.6	186.7	179.3	170.4	165.9	161.4	158.5
60°	217.2	207.6	201.6	189.7	177.1	165.9	159.2	152.5	146.6	142.8	136.9
62.5°	189.7	182.3	178.5	165.9	155.5	145.1	139.1	132.4	128.0	121.3	113.8
65°	165.9	159.9	155.5	145.1	135.4	125.7	119.8	111.6	105.6	101.9	101.2
67.5°	145.1	140.6	133.9	124.2	114.6	107.1	100.4	93.7	93.0	91.5	91.5
70°	122.0	117.5	113.8	103.4	95.2	87.0	85.6	83.3	81.1	80.3	78.9
72.5°	101.9	98.2	93.7	84.8	76.6	74.4	72.9	71.4	69.2	68.4	67.7
75°	82.6	77.4	74.4	66.2	64.0	62.5	61.0	58.8	57.3	56.5	55.1
77.5°	63.2	58.0	58.0	53.6	52.1	49.8	48.4	46.9	46.1	44.6	44.6
80°	44.6	44.6	43.1	40.9	38.7	37.9	35.7	35.0	34.2	35.0	33.5
82.5°	32.7	29.8	29.8	28.3	26.8	26.0	24.5	24.5	23.8	23.8	23.8
85°	18.6	18.6	17.9	16.4	15.6	15.6	14.9	14.9	14.1	14.1	13.4
87.5°	7.4	6.7	7.4	6.7	6.7	6.0	6.0	6.0	5.2	6.0	5.2
90°	9.2	10.4	11.5	15.3	20.6	25.2	26.0	25.2	24.4	22.9	24.4
92.5°	32.1	36.3	40.5	61.1	90.1	116.0	117.6	98.5	77.1	65.7	57.3
95°	56.5	65.6	74.8	109.9	176.3	264.9	299.2	261.8	200.0	153.4	121.4
97.5°	76.3	86.6	97.0	142.0	234.4	377.1	487.8	491.6	409.2	326.7	249.6
100°	95.4	106.1	116.8	157.3	250.4	415.3	603.1	713.0	697.0	602.3	497.7
102.5°	113.0	123.7	134.4	171.0	251.2	400.8	606.9	795.4	885.5	882.5	813.0
105°	129.8	140.5	151.2	187.0	255.0	380.9	565.7	768.7	927.5	1013.8	1023.7
107.5°	146.6	157.2	167.9	203.1	263.4	370.2	527.5	712.2	882.5	1010.7	1085.5
110°	163.4	174.4	185.5	219.1	274.1	367.2	501.5	659.6	820.6	957.3	1055.0

TEST NUMBER: P1010046

CATALOG NUMBER: S122RDIP-B485D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	179.4	190.9	202.3	234.4	285.5	368.0	484.8	622.9	764.2	893.9	1000.0
115°	197.0	207.3	217.6	250.4	297.0	371.0	473.3	593.9	719.9	837.4	937.4
117.5°	213.0	223.7	234.4	264.9	309.2	375.6	467.2	574.1	683.2	788.6	881.7
120°	229.0	239.7	250.4	280.2	321.4	380.2	461.8	558.8	657.3	751.9	832.9
122.5°	245.0	256.1	267.2	294.7	332.1	385.5	458.8	545.8	636.7	721.4	797.0
125°	260.3	271.0	281.7	309.2	343.5	390.9	455.0	533.6	616.8	695.4	762.6
127.5°	274.1	285.2	296.2	322.9	354.2	396.2	452.7	522.2	597.0	669.5	733.6
130°	287.0	297.7	308.4	335.1	364.1	402.3	451.2	510.7	577.9	643.5	703.8
132.5°	299.2	309.9	320.6	345.8	374.1	408.4	450.4	501.5	559.6	619.1	673.3
135°	309.9	320.6	331.3	355.7	382.5	413.0	449.6	493.1	542.8	593.2	643.5
137.5°	319.9	329.8	339.7	364.1	389.3	417.6	449.6	487.0	529.0	572.5	613.8
140°	328.3	338.2	348.1	371.0	394.7	420.6	448.9	481.7	516.0	552.7	587.8
142.5°	335.9	345.0	354.2	376.3	399.3	422.9	448.9	476.4	505.4	535.1	564.1
145°	344.3	352.7	361.1	381.7	403.1	424.4	447.3	471.8	495.4	520.6	544.3
147.5°	351.2	358.8	366.4	386.3	405.4	425.2	445.1	467.2	487.8	508.4	527.5
150°	358.0	364.9	371.8	389.3	406.9	424.4	442.8	461.1	479.4	496.2	512.2
152.5°	364.9	371.0	377.1	392.4	407.6	422.9	438.9	455.7	471.0	486.3	499.3
155°	371.0	376.8	382.5	395.4	408.4	421.4	434.4	448.9	463.4	475.6	487.0
157.5°	376.3	381.3	386.3	397.7	408.4	418.3	429.8	442.8	454.2	464.9	474.8
160°	381.7	385.9	390.1	399.3	408.4	416.0	425.2	435.9	445.8	454.2	462.6
162.5°	386.3	389.4	392.4	400.0	407.6	413.8	421.4	429.8	437.4	444.3	451.2
165°	389.3	391.6	393.9	400.8	406.1	410.7	416.0	422.9	429.0	434.4	439.7
167.5°	392.4	393.9	395.4	400.8	405.4	407.6	411.5	416.0	420.6	425.2	429.0
170°	393.9	395.0	396.2	400.0	403.8	405.4	407.6	410.7	414.5	416.8	419.9
172.5°	395.4	396.2	397.0	399.3	401.5	402.3	403.1	405.4	407.6	409.2	411.5
175°	396.2	396.6	397.0	398.5	400.0	399.3	400.0	400.8	403.1	403.8	404.6
177.5°	397.0	397.0	397.0	397.7	399.3	397.7	397.0	397.7	399.3	399.3	400.0
180°	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0

TEST NUMBER: P1010046

CATALOG NUMBER: S122RDIP-B485D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1024.4	1022.9	1018.4	1019.9	1017.7	1017.7	1016.2	1016.2	1016.2	1019.9	1017.7
5°	968.6	963.4	958.2	956.0	953.7	951.5	951.5	950.8	957.4	956.0	961.9
7.5°	899.4	897.9	887.5	887.5	883.8	882.3	886.0	886.8	887.5	889.0	892.7
10°	837.7	834.0	819.1	820.6	818.3	815.4	817.6	816.1	821.3	822.8	821.3
12.5°	764.8	758.1	741.7	733.5	724.6	717.9	726.1	720.1	741.0	746.9	763.3
15°	668.1	655.4	644.2	644.2	636.1	630.1	633.8	640.5	645.0	651.7	654.7
17.5°	603.3	598.1	589.2	584.0	581.8	579.5	579.5	582.5	592.2	591.4	597.4
20°	548.3	545.3	540.8	534.1	531.9	530.4	530.4	530.4	537.1	543.1	546.8
22.5°	510.3	508.1	505.1	496.2	491.7	490.3	494.0	496.2	501.4	505.9	509.6
25°	472.4	467.2	462.0	459.0	456.8	456.8	458.3	459.0	461.2	463.5	467.9
27.5°	441.2	437.4	430.0	421.8	421.8	419.6	421.1	422.6	427.8	435.2	438.9
30°	406.2	405.4	402.5	399.5	396.5	395.0	398.0	400.2	401.0	404.7	404.7
32.5°	380.9	375.7	370.5	367.5	366.0	365.3	366.0	369.0	369.0	373.5	378.7
35°	355.6	352.6	347.4	342.2	340.7	337.0	340.0	343.0	348.2	350.4	352.6
37.5°	328.1	324.4	322.1	320.6	317.7	318.4	316.2	320.6	325.1	324.4	325.8
40°	307.2	300.6	293.9	293.1	292.4	291.6	291.6	292.4	295.3	298.3	302.8
42.5°	280.5	278.2	272.3	266.3	264.8	263.4	261.9	264.8	270.8	276.0	278.2
45°	252.9	250.0	248.5	244.0	241.0	240.3	238.8	242.5	247.7	250.0	251.5
47.5°	227.6	226.9	222.4	223.2	220.9	221.7	220.9	223.2	223.2	225.4	226.9
50°	210.5	208.3	206.1	204.6	202.4	202.4	201.6	202.4	205.3	208.3	207.6
52.5°	193.4	189.7	189.0	188.2	186.7	188.2	186.0	186.7	189.7	191.2	190.4
55°	173.3	172.6	171.1	169.6	168.9	168.1	168.1	168.1	171.1	173.3	174.1
57.5°	157.7	154.0	151.0	151.0	148.0	147.3	148.8	149.5	151.8	153.3	154.7
60°	136.1	134.7	130.2	128.0	123.5	122.7	122.7	125.7	129.4	134.7	136.1
62.5°	113.1	110.8	110.1	110.1	110.1	110.1	110.1	110.1	110.1	110.8	110.8
65°	100.4	101.2	100.4	99.7	100.4	100.4	99.7	99.7	99.7	100.4	101.2
67.5°	90.0	89.3	90.0	89.3	88.5	88.5	87.8	88.5	89.3	90.0	90.0
70°	78.1	78.1	77.4	78.1	77.4	76.6	75.9	75.9	77.4	78.1	78.1
72.5°	67.0	67.0	66.2	66.2	64.7	64.7	65.5	64.7	64.7	67.0	67.0
75°	55.8	55.1	54.3	54.3	53.6	53.6	53.6	52.8	54.3	54.3	55.1
77.5°	43.9	43.9	43.9	43.1	43.1	42.4	42.4	43.1	43.1	43.1	43.9
80°	33.5	33.5	33.5	32.7	32.0	32.0	32.0	32.0	32.0	32.7	32.0
82.5°	23.1	23.1	23.1	23.1	23.1	22.3	22.3	22.3	23.1	23.1	22.3
85°	14.1	13.4	14.1	14.1	13.4	14.1	13.4	13.4	12.6	12.6	13.4
87.5°	6.0	5.2	4.5	4.5	5.2	4.5	4.5	4.5	5.2	4.5	4.5
90°	24.8	25.2	25.2	25.2	25.2	25.2	25.2	25.2	25.2	25.2	24.8
92.5°	54.2	51.1	50.4	47.3	48.1	46.6	48.1	47.3	50.4	51.1	54.2
95°	113.0	104.6	94.7	88.6	86.3	87.0	86.3	88.6	94.7	104.6	113.0
97.5°	226.7	203.8	174.1	158.8	150.4	145.8	150.4	158.8	174.1	203.8	226.7
100°	451.6	405.4	342.0	309.2	287.0	273.3	287.0	309.2	342.0	405.4	451.6
102.5°	763.4	713.8	643.5	581.7	552.7	532.8	552.7	581.7	643.5	713.8	763.4
105°	1011.1	998.5	951.2	903.9	871.0	860.3	871.0	903.9	951.2	998.5	1011.1
107.5°	1100.8	1116.1	1115.3	1108.4	1098.5	1081.0	1098.5	1108.4	1115.3	1116.1	1100.8
110°	1086.3	1117.6	1150.4	1164.9	1171.8	1171.0	1171.8	1164.9	1150.4	1117.6	1086.3

TEST NUMBER: P1010046

CATALOG NUMBER: S122RDIP-B485D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1037.0	1074.1	1122.9	1149.7	1164.2	1169.5	1164.2	1149.7	1122.9	1074.1	1037.0
115°	976.8	1016.1	1070.3	1105.4	1125.2	1132.1	1125.2	1105.4	1070.3	1016.1	976.8
117.5°	919.1	956.5	1012.3	1049.7	1070.3	1075.6	1070.3	1049.7	1012.3	956.5	919.1
120°	867.6	902.3	955.8	991.6	1013.8	1021.4	1013.8	991.6	955.8	902.3	867.6
122.5°	827.5	858.0	904.6	939.7	958.8	964.9	958.8	939.7	904.6	858.0	827.5
125°	791.2	819.9	864.2	893.2	912.2	918.4	912.2	893.2	864.2	819.9	791.2
127.5°	760.4	787.1	826.0	853.5	870.3	874.8	870.3	853.5	826.0	787.1	760.4
130°	729.0	754.2	791.6	817.6	832.9	839.0	832.9	817.6	791.6	754.2	729.0
132.5°	696.6	719.9	756.5	782.5	796.2	801.6	796.2	782.5	756.5	719.9	696.6
135°	664.9	686.3	719.1	744.3	758.0	761.1	758.0	744.3	719.1	686.3	664.9
137.5°	632.8	651.9	683.2	705.4	717.6	722.2	717.6	705.4	683.2	651.9	632.8
140°	604.6	621.4	645.8	665.7	677.1	681.7	677.1	665.7	645.8	621.4	604.6
142.5°	577.5	590.9	613.8	631.3	641.2	641.2	641.2	631.3	613.8	590.9	577.5
145°	555.3	566.4	584.8	597.7	605.4	607.7	605.4	597.7	584.8	566.4	555.3
147.5°	535.9	544.3	560.3	571.0	576.4	577.9	576.4	571.0	560.3	544.3	535.9
150°	519.1	526.0	537.4	546.6	551.2	551.9	551.2	546.6	537.4	526.0	519.1
152.5°	505.0	510.7	519.1	526.7	529.8	529.8	529.8	526.7	519.1	510.7	505.0
155°	491.2	495.4	503.8	509.2	512.2	510.7	512.2	509.2	503.8	495.4	491.2
157.5°	478.2	481.7	487.8	492.4	493.9	493.9	493.9	492.4	487.8	481.7	478.2
160°	465.3	468.0	473.3	477.1	477.9	477.9	477.9	477.1	473.3	468.0	465.3
162.5°	453.1	455.0	460.3	462.6	463.4	462.6	463.4	462.6	460.3	455.0	453.1
165°	441.2	442.8	445.8	448.9	448.9	448.1	448.9	448.9	445.8	442.8	441.2
167.5°	430.6	432.1	433.6	435.1	435.1	434.4	435.1	435.1	433.6	432.1	430.6
170°	420.6	421.4	422.2	424.4	423.7	422.2	423.7	424.4	422.2	421.4	420.6
172.5°	411.8	412.2	413.0	413.8	413.0	412.2	413.0	413.8	413.0	412.2	411.8
175°	405.0	405.4	405.4	406.1	405.4	403.8	405.4	406.1	405.4	405.4	405.0
177.5°	400.0	400.0	400.0	400.0	399.3	397.7	399.3	400.0	400.0	400.0	400.0
180°	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0

TEST NUMBER: P1010046

CATALOG NUMBER: S122RDIP-B485D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1019.9	1023.7	1022.2	1014.0	1022.2	1024.4	1028.9	1033.3	1036.3	1040.8	1044.5
5°	956.0	963.4	967.9	963.4	978.3	980.5	990.9	996.9	1005.8	1013.2	1019.2
7.5°	895.7	901.7	910.6	912.1	921.0	931.4	946.3	961.2	975.3	982.7	989.4
10°	831.0	841.4	854.8	851.8	865.2	881.6	897.2	921.0	932.9	946.3	958.2
12.5°	766.3	773.0	790.8	796.8	816.1	828.7	850.3	865.2	895.0	910.6	921.0
15°	653.2	680.7	703.0	729.8	755.1	778.9	798.2	825.0	851.1	863.0	880.1
17.5°	601.8	614.5	627.9	641.3	674.0	716.4	750.6	779.6	802.0	817.6	837.7
20°	548.3	560.9	575.8	588.5	608.5	639.0	681.4	731.3	758.1	774.4	793.8
22.5°	510.3	522.2	531.9	543.1	558.7	581.0	613.0	674.8	710.5	730.5	747.7
25°	469.4	484.3	494.7	502.9	515.5	540.1	566.1	601.1	665.1	680.7	704.5
27.5°	441.2	445.6	457.5	470.2	482.8	496.2	523.0	552.7	595.9	630.1	659.1
30°	407.7	418.8	430.0	435.2	446.4	465.7	482.1	514.1	547.5	574.3	609.3
32.5°	382.4	389.1	396.5	409.2	419.6	433.0	449.3	476.1	504.4	521.5	548.3
35°	354.1	358.6	374.2	379.4	389.8	403.2	419.6	440.4	470.9	484.3	503.6
37.5°	327.3	337.7	342.2	354.1	363.8	377.2	389.1	412.9	433.0	448.6	466.4
40°	306.5	311.0	319.1	329.6	337.7	348.2	363.0	380.2	401.7	414.4	430.0
42.5°	281.2	284.9	295.3	301.3	314.7	324.4	333.3	354.1	373.5	383.1	398.8
45°	253.7	262.6	269.3	281.2	288.6	300.6	311.7	326.6	344.4	355.6	364.5
47.5°	229.9	238.8	245.5	256.7	268.6	273.8	285.7	301.3	317.7	326.6	339.2
50°	210.5	213.5	226.2	231.4	244.0	254.4	262.6	276.0	293.9	299.1	309.5
52.5°	191.9	194.2	202.4	209.0	220.2	229.1	239.5	252.2	267.1	275.3	283.4
55°	175.6	177.1	180.8	188.2	195.7	206.8	216.5	228.4	241.0	250.0	257.4
57.5°	157.0	159.9	162.9	167.4	174.8	185.2	195.7	206.8	217.2	223.2	232.9
60°	135.4	139.9	145.1	150.3	155.5	162.9	174.8	185.2	194.9	200.1	207.6
62.5°	112.3	121.3	125.7	131.7	136.1	142.8	151.8	163.7	170.4	177.1	183.0
65°	101.2	101.9	102.7	108.6	116.8	123.5	131.7	140.6	151.0	155.5	159.9
67.5°	90.0	90.8	92.2	93.0	96.0	103.4	112.3	122.0	130.2	133.2	137.6
70°	78.9	78.9	81.8	82.6	83.3	84.1	91.5	101.2	108.6	112.3	117.5
72.5°	67.0	67.7	69.2	69.9	71.4	72.9	75.1	80.3	89.3	93.0	98.9
75°	55.1	55.8	56.5	57.3	59.5	60.3	62.5	65.5	69.2	73.6	77.4
77.5°	43.9	43.9	44.6	46.1	47.6	48.4	50.6	52.1	53.6	55.8	58.8
80°	32.7	33.5	33.5	35.0	35.0	35.7	36.5	38.7	40.2	41.7	43.1
82.5°	22.3	23.8	23.8	23.8	24.5	25.3	26.0	26.0	27.5	28.3	30.5
85°	13.4	14.1	14.1	14.1	13.4	14.9	14.9	15.6	15.6	15.6	16.4
87.5°	5.2	4.5	5.2	5.2	5.2	6.0	5.2	5.2	6.0	6.7	6.7
90°	24.4	22.9	24.4	25.2	26.0	25.2	20.6	15.3	11.5	10.4	9.2
92.5°	57.3	65.7	77.1	98.5	117.6	116.0	90.1	61.1	40.5	36.3	32.1
95°	121.4	153.4	200.0	261.8	299.2	264.9	176.3	109.9	74.8	65.6	56.5
97.5°	249.6	326.7	409.2	491.6	487.8	377.1	234.4	142.0	97.0	86.6	76.3
100°	497.7	602.3	697.0	713.0	603.1	415.3	250.4	157.3	116.8	106.1	95.4
102.5°	813.0	882.5	885.5	795.4	606.9	400.8	251.2	171.0	134.4	123.7	113.0
105°	1023.7	1013.8	927.5	768.7	565.7	380.9	255.0	187.0	151.2	140.5	129.8
107.5°	1085.5	1010.7	882.5	712.2	527.5	370.2	263.4	203.1	167.9	157.2	146.6
110°	1055.0	957.3	820.6	659.6	501.5	367.2	274.1	219.1	185.5	174.4	163.4

TEST NUMBER: P1010046

CATALOG NUMBER: S122RDIP-B485D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1000.0	893.9	764.2	622.9	484.8	368.0	285.5	234.4	202.3	190.9	179.4
115°	937.4	837.4	719.9	593.9	473.3	371.0	297.0	250.4	217.6	207.3	197.0
117.5°	881.7	788.6	683.2	574.1	467.2	375.6	309.2	264.9	234.4	223.7	213.0
120°	832.9	751.9	657.3	558.8	461.8	380.2	321.4	280.2	250.4	239.7	229.0
122.5°	797.0	721.4	636.7	545.8	458.8	385.5	332.1	294.7	267.2	256.1	245.0
125°	762.6	695.4	616.8	533.6	455.0	390.9	343.5	309.2	281.7	271.0	260.3
127.5°	733.6	669.5	597.0	522.2	452.7	396.2	354.2	322.9	296.2	285.2	274.1
130°	703.8	643.5	577.9	510.7	451.2	402.3	364.1	335.1	308.4	297.7	287.0
132.5°	673.3	619.1	559.6	501.5	450.4	408.4	374.1	345.8	320.6	309.9	299.2
135°	643.5	593.2	542.8	493.1	449.6	413.0	382.5	355.7	331.3	320.6	309.9
137.5°	613.8	572.5	529.0	487.0	449.6	417.6	389.3	364.1	339.7	329.8	319.9
140°	587.8	552.7	516.0	481.7	448.9	420.6	394.7	371.0	348.1	338.2	328.3
142.5°	564.1	535.1	505.4	476.4	448.9	422.9	399.3	376.3	354.2	345.0	335.9
145°	544.3	520.6	495.4	471.8	447.3	424.4	403.1	381.7	361.1	352.7	344.3
147.5°	527.5	508.4	487.8	467.2	445.1	425.2	405.4	386.3	366.4	358.8	351.2
150°	512.2	496.2	479.4	461.1	442.8	424.4	406.9	389.3	371.8	364.9	358.0
152.5°	499.3	486.3	471.0	455.7	438.9	422.9	407.6	392.4	377.1	371.0	364.9
155°	487.0	475.6	463.4	448.9	434.4	421.4	408.4	395.4	382.5	376.8	371.0
157.5°	474.8	464.9	454.2	442.8	429.8	418.3	408.4	397.7	386.3	381.3	376.3
160°	462.6	454.2	445.8	435.9	425.2	416.0	408.4	399.3	390.1	385.9	381.7
162.5°	451.2	444.3	437.4	429.8	421.4	413.8	407.6	400.0	392.4	389.4	386.3
165°	439.7	434.4	429.0	422.9	416.0	410.7	406.1	400.8	393.9	391.6	389.3
167.5°	429.0	425.2	420.6	416.0	411.5	407.6	405.4	400.8	395.4	393.9	392.4
170°	419.9	416.8	414.5	410.7	407.6	405.4	403.8	400.0	396.2	395.0	393.9
172.5°	411.5	409.2	407.6	405.4	403.1	402.3	401.5	399.3	397.0	396.2	395.4
175°	404.6	403.8	403.1	400.8	400.0	399.3	400.0	398.5	397.0	396.6	396.2
177.5°	400.0	399.3	399.3	397.7	397.0	397.7	399.3	397.7	397.0	397.0	397.0
180°	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0

TEST NUMBER: P1010046

CATALOG NUMBER: S122RDIP-B485D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1070.5	1070.5	1070.5	1070.5
2.5°	1051.2	1049.0	1062.3	1077.2
5°	1029.6	1033.3	1050.4	1071.3
7.5°	1007.3	1015.5	1035.6	1063.1
10°	976.0	990.9	1021.4	1049.7
12.5°	945.5	965.6	994.6	1028.1
15°	911.3	933.6	969.3	1009.5
17.5°	873.4	898.7	940.3	984.2
20°	833.2	866.7	910.6	958.2
22.5°	788.6	828.7	874.1	926.9
25°	745.4	789.3	834.7	895.7
27.5°	703.0	746.2	796.8	858.5
30°	660.6	700.0	754.4	820.6
32.5°	615.2	656.2	713.4	781.1
35°	573.6	614.5	668.1	735.0
37.5°	528.9	572.8	624.2	693.3
40°	476.9	528.2	578.0	644.2
42.5°	433.7	488.0	536.4	598.9
45°	399.5	450.8	491.0	552.0
47.5°	367.5	409.2	450.1	506.6
50°	337.0	369.0	411.4	462.0
52.5°	305.8	333.3	369.7	417.3
55°	277.5	303.5	336.3	372.7
57.5°	251.5	270.0	302.8	335.5
60°	222.4	241.8	267.1	294.6
62.5°	197.9	212.8	236.6	259.6
65°	171.8	186.0	203.8	225.4
67.5°	148.0	160.7	174.8	191.9
70°	126.5	136.1	146.6	161.4
72.5°	103.4	113.8	123.5	135.4
75°	84.8	89.3	97.5	105.6
77.5°	65.5	71.4	75.9	82.6
80°	46.9	52.1	53.6	58.8
82.5°	31.2	34.2	37.2	38.7
85°	17.9	19.3	22.3	23.1
87.5°	6.7	7.4	8.9	10.4
90°	7.6	6.1	3.1	0.8
92.5°	26.0	22.1	16.0	11.5
95°	44.3	37.4	29.8	26.7
97.5°	62.6	52.7	44.3	39.7
100°	80.2	67.9	61.1	58.8
102.5°	97.0	84.7	77.9	76.3
105°	113.0	101.5	96.2	93.1
107.5°	129.8	119.1	113.7	111.5
110°	147.3	137.4	132.8	129.8

TEST NUMBER: P1010046

CATALOG NUMBER: S122RDIP-B485D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	164.1	155.0	149.6	146.6
115°	181.7	172.5	167.9	164.1
117.5°	198.5	190.1	185.5	182.4
120°	213.7	206.9	202.3	199.2
122.5°	229.8	222.1	217.6	215.3
125°	245.0	235.9	231.3	229.0
127.5°	259.6	249.6	243.5	240.5
130°	271.8	261.1	253.4	250.4
132.5°	283.2	271.8	263.4	259.6
135°	292.4	280.9	271.8	268.7
137.5°	302.3	290.1	280.9	277.1
140°	311.5	299.2	290.1	287.0
142.5°	319.9	307.6	299.2	297.0
145°	329.0	317.6	309.9	306.9
147.5°	338.2	327.5	319.9	317.6
150°	346.6	336.7	330.5	328.3
152.5°	354.2	345.8	339.7	338.9
155°	362.6	354.2	349.6	348.9
157.5°	369.5	361.8	358.0	357.3
160°	375.6	369.5	366.4	365.7
162.5°	380.9	376.3	373.3	374.1
165°	385.5	380.9	379.4	380.2
167.5°	389.3	386.3	384.7	385.5
170°	392.4	390.1	389.3	390.9
172.5°	394.7	392.4	393.1	393.9
175°	396.2	394.7	395.4	396.2
177.5°	397.0	395.4	396.2	397.7
180°	397.0	397.0	397.0	397.0

(END OF REPORT)