

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010064

Luminaire Tested: S122RDIP-B485D725UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010064
REPORT IS A COMBINATION OF REPORTS P988374 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B485D725UB50-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4439.0 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010064

CATALOG NUMBER: S122RDIP-B485D725UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1010064

CATALOG NUMBER: S122RDIP-B485D725UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	96	92	89	85	87	84	81	78	69	67	65	55	54	53	42	42	41
2	88	81	76	71	80	74	69	65	61	58	55	49	47	45	38	37	35
3	81	72	65	60	73	66	60	55	55	50	47	44	41	39	34	33	31
4	74	64	57	51	67	59	52	48	49	44	41	40	37	34	31	29	27
5	68	57	50	44	62	53	46	41	44	39	35	36	33	30	29	26	24
6	63	52	44	39	58	48	41	36	40	35	31	33	29	26	26	24	22
7	59	47	39	34	53	43	37	32	37	32	28	30	26	24	24	22	20
8	54	43	35	30	50	40	33	29	33	29	25	28	24	21	22	20	18
9	51	39	32	27	46	36	30	26	31	26	23	26	22	19	21	18	16
10	48	36	29	25	44	33	27	23	29	24	20	24	20	18	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16287	16287	16287	16287
5°	16324	17299	16381	13820
10°	16144	18284	16259	11412
15°	15794	18290	16062	8573
20°	15373	15118	15707	7073
25°	14861	9446	15182	6017
30°	14209	6048	14596	5181
35°	13416	4648	13851	4433
40°	12532	3907	13066	3878
45°	11586	3325	12071	3255
50°	10618	2826	11113	2816
55°	9545	2455	10059	2424
60°	8591	1872	9046	1850
65°	7700	1409	8159	1598
70°	6721	1125	7245	1302
75°	5678	861	6198	986
80°	4511	587	4854	645
85°	3136	303	3433	320

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 14898 cd/sqm

TEST NUMBER: P1010064

CATALOG NUMBER: S122RDIP-B485D725UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.6	2.2
10°-20°	272.4	6.1
20°-30°	350.6	7.9
30°-40°	332.6	7.5
40°-50°	285.0	6.4
50°-60°	217.1	4.9
60°-70°	136.9	3.1
70°-80°	68.3	1.5
80°-90°	20.0	0.5
90°-100°	148.8	3.4
100°-110°	524.1	11.8
110°-120°	550.4	12.4
120°-130°	452.8	10.2
130°-140°	363.8	8.2
140°-150°	274.8	6.2
150°-160°	193.2	4.4
160°-170°	113.7	2.6
170°-180°	37.0	0.8
0°-30°	720.6	16.2
0°-40°	1053.1	23.7
0°-60°	1555.3	35.0
0°-90°	1780.5	40.1
90°-120°	1223.3	27.6
90°-150°	2314.7	52.1
90°-180°	2659.0	59.9
0°-180°	4439.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1029	1029	1029	1029	1029	
5°	1030	1145	1033	914	1030	98
15°	970	1292	987	606	970	273
25°	861	689	879	439	861	395
35°	706	340	729	324	706	442
45°	530	236	553	231	530	409
55°	358	164	378	162	358	323
65°	217	85	230	96	217	215
75°	102	45	111	52	102	110
85°	22	13	24	14	22	25
90°	1	24	1	24	1	3
95°	26	84	26	84	26	27
105°	90	827	90	827	90	95
115°	158	1089	158	1089	158	157
125°	220	883	220	883	220	196
135°	258	732	258	732	258	200
145°	295	584	295	584	295	185
155°	336	491	336	491	336	154
165°	366	431	366	431	366	103
175°	381	388	381	388	381	36
180°	382	382	382	382	382	

TEST NUMBER: P1010064

CATALOG NUMBER: S122RDIP-B485D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9
2.5°	1035.3	1039.6	1041.7	1044.6	1051.0	1055.3	1061.8	1063.2	1062.5	1065.3	1057.5
5°	1029.6	1038.9	1047.5	1054.6	1066.0	1073.2	1081.1	1090.3	1092.5	1103.2	1096.8
7.5°	1021.7	1035.3	1047.5	1061.8	1078.9	1088.2	1100.4	1114.7	1121.1	1134.0	1137.5
10°	1008.8	1028.1	1048.9	1063.9	1087.5	1103.9	1115.4	1138.3	1153.3	1172.6	1169.7
12.5°	988.1	1013.1	1041.0	1066.0	1096.8	1107.5	1129.0	1152.6	1171.9	1189.7	1205.5
15°	970.2	998.8	1029.6	1060.3	1095.4	1115.4	1136.8	1167.6	1188.3	1219.8	1233.3
17.5°	945.9	982.4	1018.9	1053.2	1094.6	1117.5	1144.0	1174.0	1204.7	1234.8	1245.5
20°	920.9	960.2	999.5	1046.0	1093.2	1115.4	1142.5	1179.7	1209.8	1233.3	1233.3
22.5°	890.9	938.8	983.8	1028.1	1079.6	1111.8	1139.7	1183.3	1204.7	1209.8	1190.4
25°	860.8	908.7	958.1	1013.1	1071.8	1100.4	1131.8	1172.6	1179.7	1159.7	1109.7
27.5°	825.1	878.7	934.5	993.8	1055.3	1091.1	1119.7	1146.8	1133.2	1079.6	1001.7
30°	788.6	846.5	909.5	965.9	1040.3	1073.2	1097.5	1105.4	1062.5	975.2	874.4
32.5°	750.7	807.2	873.7	941.6	1016.7	1048.2	1063.9	1043.2	964.5	854.4	731.4
35°	706.4	770.0	839.4	910.2	984.5	1008.1	1017.4	966.7	865.8	723.6	601.3
37.5°	666.4	730.0	804.4	876.6	948.8	961.7	952.4	873.0	745.0	604.2	484.8
40°	619.2	687.1	760.0	840.8	900.2	903.7	880.9	777.9	619.2	486.9	413.3
42.5°	575.6	644.2	717.1	799.4	844.4	832.2	801.5	666.4	516.9	419.7	360.4
45°	530.5	595.6	674.2	747.2	779.3	750.7	704.3	560.5	434.0	361.1	315.3
47.5°	486.9	547.7	625.6	695.7	701.4	669.2	614.2	469.7	376.1	317.5	280.3
50°	444.0	504.8	577.7	635.6	629.9	585.6	523.4	408.3	326.7	280.3	249.5
52.5°	401.1	456.2	526.9	572.7	548.4	505.5	444.0	346.1	285.3	244.5	220.9
55°	358.2	409.7	470.5	508.4	469.7	420.4	376.8	296.7	247.4	214.5	196.6
57.5°	322.5	363.2	419.0	441.9	395.4	356.8	318.9	255.2	214.5	190.9	170.2
60°	283.1	320.3	366.1	379.7	331.8	300.3	268.1	215.9	183.8	163.0	149.4
62.5°	249.5	280.3	315.3	315.3	273.1	249.5	225.2	180.9	154.4	138.0	131.6
65°	216.6	238.8	263.8	261.0	225.2	204.5	185.2	149.4	129.4	118.0	111.5
67.5°	184.5	201.6	218.1	208.1	182.3	164.4	146.6	120.8	107.2	99.4	90.8
70°	155.2	168.7	177.3	168.0	142.3	127.3	114.4	97.2	86.5	76.5	71.5
72.5°	130.1	135.8	138.7	127.3	105.8	97.2	87.9	75.8	66.5	61.5	60.1
75°	101.5	106.5	104.4	95.8	77.9	71.5	64.3	55.8	53.6	50.8	49.3
77.5°	79.4	79.4	75.8	67.9	55.8	50.8	47.9	43.6	41.5	40.8	39.3
80°	56.5	55.8	53.6	45.0	37.9	35.0	35.0	32.2	31.5	30.0	30.0
82.5°	37.2	37.2	34.3	27.2	25.0	24.3	23.6	22.2	22.2	21.4	21.4
85°	22.2	20.7	17.2	15.0	14.3	14.3	13.6	12.9	13.6	12.9	12.9
87.5°	10.0	7.9	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7
90°	0.7	2.9	5.9	7.3	8.8	9.9	11.0	14.7	19.8	24.2	25.0
92.5°	11.0	15.4	21.3	25.0	30.8	34.8	38.9	58.7	86.6	111.6	113.1
95°	25.7	28.6	36.0	42.6	54.3	63.1	71.9	105.7	169.6	254.7	287.8
97.5°	38.2	42.6	50.7	60.2	73.4	83.3	93.2	136.6	225.4	362.7	469.1
100°	56.5	58.7	65.3	77.1	91.8	102.0	112.3	151.2	240.8	399.4	580.0
102.5°	73.4	74.9	81.5	93.2	108.7	119.0	129.2	164.4	241.5	385.4	583.6
105°	89.6	92.5	97.6	108.7	124.8	135.1	145.4	179.9	245.2	366.3	544.0
107.5°	107.2	109.4	114.5	124.8	141.0	151.2	161.5	195.3	253.3	356.1	507.3
110°	124.8	127.7	132.1	141.7	157.1	167.8	178.4	210.7	263.6	353.1	482.3

TEST NUMBER: P1010064

CATALOG NUMBER: S122RDIP-B485D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	141.0	143.9	149.0	157.8	172.5	183.5	194.5	225.4	274.6	353.9	466.2
115°	157.8	161.5	165.9	174.7	189.4	199.3	209.2	240.8	285.6	356.8	455.2
117.5°	175.5	178.4	182.8	190.9	204.8	215.1	225.4	254.7	297.3	361.2	449.3
120°	191.6	194.5	199.0	205.6	220.2	230.5	240.8	269.4	309.1	365.6	444.2
122.5°	207.0	209.2	213.6	221.0	235.7	246.3	256.9	283.4	319.4	370.7	441.2
125°	220.2	222.4	226.9	235.7	250.3	260.6	270.9	297.3	330.4	375.9	437.5
127.5°	231.3	234.2	240.1	249.6	263.6	274.2	284.8	310.5	340.6	381.0	435.3
130°	240.8	243.7	251.1	261.4	276.0	286.3	296.6	322.3	350.2	386.9	433.9
132.5°	249.6	253.3	261.4	272.4	287.8	298.0	308.3	332.6	359.7	392.8	433.1
135°	258.4	261.4	270.2	281.2	298.1	308.4	318.6	342.1	367.8	397.2	432.4
137.5°	266.5	270.2	279.0	290.7	307.6	317.2	326.7	350.2	374.4	401.6	432.4
140°	276.0	279.0	287.8	299.5	315.7	325.2	334.8	356.8	379.6	404.5	431.7
142.5°	285.6	287.8	295.9	307.6	323.0	331.8	340.6	361.9	384.0	406.7	431.7
145°	295.1	298.1	305.4	316.4	331.1	339.2	347.2	367.1	387.6	408.2	430.2
147.5°	305.4	307.6	314.9	325.2	337.7	345.0	352.4	371.5	389.8	408.9	428.0
150°	315.7	317.9	323.8	333.3	344.3	350.9	357.5	374.4	391.3	408.2	425.8
152.5°	326.0	326.7	332.6	340.6	350.9	356.8	362.7	377.3	392.0	406.7	422.1
155°	335.5	336.2	340.6	348.7	356.8	362.3	367.8	380.3	392.8	405.2	417.7
157.5°	343.6	344.3	348.0	355.3	361.9	366.7	371.5	382.5	392.8	402.3	413.3
160°	351.7	352.4	355.3	361.2	367.1	371.1	375.1	384.0	392.8	400.1	408.9
162.5°	359.7	359.0	361.9	366.3	371.5	374.4	377.3	384.7	392.0	397.9	405.2
165°	365.6	364.9	366.3	370.7	374.4	376.6	378.8	385.4	390.6	395.0	400.1
167.5°	370.7	370.0	371.5	374.4	377.3	378.8	380.3	385.4	389.8	392.0	395.7
170°	375.9	374.4	375.1	377.3	378.8	379.9	381.0	384.7	388.4	389.8	392.0
172.5°	378.8	378.1	377.3	379.6	380.3	381.0	381.8	384.0	386.2	386.9	387.6
175°	381.0	380.3	379.6	381.0	381.0	381.4	381.8	383.2	384.7	384.0	384.7
177.5°	382.5	381.0	380.3	381.8	381.8	381.8	381.8	382.5	384.0	382.5	381.8
180°	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8

TEST NUMBER: P1010064

CATALOG NUMBER: S122RDIP-B485D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9
2.5°	1065.3	1066.8	1068.9	1078.9	1080.3	1083.2	1081.8	1081.8	1082.5	1081.1	1081.8
5°	1111.1	1113.2	1124.0	1136.1	1139.0	1136.1	1139.7	1144.7	1144.7	1144.7	1143.3
7.5°	1154.0	1161.8	1174.0	1191.9	1195.5	1199.0	1205.5	1201.2	1202.6	1209.0	1206.9
10°	1195.5	1206.9	1220.5	1235.5	1243.4	1248.4	1251.2	1257.7	1272.7	1255.5	1261.9
12.5°	1234.8	1251.2	1265.5	1282.0	1287.7	1294.1	1296.3	1302.0	1302.0	1301.3	1306.3
15°	1260.5	1275.5	1288.4	1299.1	1300.6	1299.1	1297.7	1298.4	1300.6	1292.0	1297.0
17.5°	1266.2	1267.7	1272.0	1267.7	1268.4	1253.4	1244.8	1242.6	1222.6	1223.3	1239.8
20°	1238.4	1214.0	1207.6	1184.0	1169.7	1131.1	1129.7	1118.9	1076.8	1089.6	1086.8
22.5°	1161.8	1120.4	1065.3	1038.2	1024.6	983.8	952.4	930.2	915.2	900.2	893.7
25°	1061.0	993.8	915.9	862.3	854.4	816.5	758.6	731.4	699.3	689.2	706.4
27.5°	930.9	843.7	755.7	673.5	658.5	624.2	594.9	575.6	538.4	536.2	537.7
30°	754.3	666.4	592.7	539.1	501.9	486.2	466.9	452.6	437.6	443.3	444.7
32.5°	619.9	536.2	467.6	439.0	421.8	411.8	395.4	386.1	379.7	377.5	376.8
35°	492.6	436.9	406.1	378.2	368.2	361.1	348.9	344.6	338.9	339.6	339.6
37.5°	421.8	375.4	352.5	338.2	328.9	325.3	317.5	313.2	309.6	308.2	310.3
40°	363.9	331.8	317.5	304.6	296.7	295.3	291.0	286.0	281.7	282.4	284.6
42.5°	321.7	303.2	286.0	276.0	270.3	268.1	264.5	261.0	261.0	258.8	258.1
45°	288.1	273.1	258.8	249.5	246.0	243.1	238.8	238.1	235.2	235.9	236.7
47.5°	258.1	246.0	235.2	225.9	222.4	221.6	217.4	214.5	214.5	213.8	213.1
50°	230.9	218.8	209.5	204.5	199.5	198.1	197.3	196.6	195.2	195.2	195.9
52.5°	208.8	196.6	189.5	185.2	182.3	180.9	180.9	180.2	180.2	180.2	179.5
55°	184.5	174.5	168.7	167.3	165.9	165.2	164.4	163.0	162.3	163.7	162.3
57.5°	161.6	158.0	153.0	151.6	148.0	148.0	145.9	144.4	143.0	144.4	144.4
60°	143.7	138.7	135.8	131.6	128.7	125.8	122.3	121.5	120.1	119.4	118.7
62.5°	125.1	120.8	113.7	107.2	103.0	100.1	98.7	98.0	98.0	97.2	97.2
65°	104.4	94.4	90.8	88.7	87.9	87.2	85.8	85.1	85.8	85.1	85.8
67.5°	81.5	80.1	77.9	76.5	75.8	75.1	75.1	74.4	74.4	74.4	74.4
70°	70.8	67.2	66.5	65.1	65.1	64.3	64.3	64.3	64.3	63.6	65.1
72.5°	58.6	56.5	55.8	55.1	55.1	55.1	54.3	54.3	54.3	53.6	54.3
75°	47.9	47.2	45.8	45.8	45.0	45.8	45.0	45.0	44.3	45.0	45.0
77.5°	38.6	37.9	37.2	37.2	36.5	36.5	36.5	36.5	36.5	36.5	37.2
80°	29.3	28.6	27.9	28.6	27.9	28.6	27.9	27.9	28.6	27.9	27.9
82.5°	21.4	20.7	20.7	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0
85°	12.9	12.2	12.2	12.9	12.2	12.9	12.2	12.2	12.2	12.9	12.9
87.5°	5.7	6.4	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	6.4
90°	24.2	23.5	22.0	23.5	23.8	24.2	24.2	24.2	24.2	24.2	24.2
92.5°	94.7	74.1	63.1	55.1	52.2	49.2	48.5	45.5	46.3	44.8	46.3
95°	251.8	192.3	147.6	116.7	108.6	100.6	91.0	85.2	83.0	83.7	83.0
97.5°	472.8	393.5	314.2	240.1	218.0	196.0	167.4	152.7	144.6	140.2	144.6
100°	685.7	670.3	579.2	478.7	434.2	389.8	328.9	297.3	276.0	262.8	276.0
102.5°	765.0	851.6	848.7	781.9	734.2	686.4	618.9	559.4	531.5	512.4	531.5
105°	739.3	892.0	974.9	984.5	972.4	960.3	914.7	869.2	837.7	827.4	837.7
107.5°	685.0	848.7	972.0	1044.0	1058.6	1073.3	1072.6	1066.0	1056.4	1039.5	1056.4
110°	634.3	789.2	920.6	1014.6	1044.7	1074.8	1106.4	1120.3	1126.9	1126.2	1126.9

TEST NUMBER: P1010064

CATALOG NUMBER: S122RDIP-B485D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	599.1	734.9	859.7	961.7	997.3	1032.9	1079.9	1105.6	1119.6	1124.7	1119.6
115°	571.2	692.3	805.4	901.5	939.3	977.1	1029.3	1063.0	1082.1	1088.7	1082.1
117.5°	552.1	657.1	758.4	847.9	883.9	919.9	973.5	1009.4	1029.3	1034.4	1029.3
120°	537.4	632.1	723.1	800.9	834.4	867.8	919.1	953.7	974.9	982.3	974.9
122.5°	524.9	612.3	693.8	766.4	795.8	825.2	870.0	903.7	922.1	928.0	922.1
125°	513.2	593.2	668.8	733.4	761.0	788.5	831.0	858.9	877.3	883.2	877.3
127.5°	502.2	574.1	643.8	705.5	731.2	756.9	794.3	820.8	836.9	841.3	836.9
130°	491.1	555.7	618.9	676.9	701.1	725.3	761.3	786.3	800.9	806.8	800.9
132.5°	482.3	538.1	595.4	647.5	669.9	692.3	727.5	752.5	765.7	770.8	765.7
135°	474.3	522.0	570.4	618.9	639.4	660.0	691.6	715.8	729.0	731.9	729.0
137.5°	468.4	508.8	550.6	590.3	608.6	627.0	657.1	678.3	690.1	694.5	690.1
140°	463.2	496.3	531.5	565.3	581.4	597.6	621.1	640.2	651.2	655.6	651.2
142.5°	458.1	486.0	514.6	542.5	555.4	568.2	590.3	607.1	616.7	616.7	616.7
145°	453.7	476.5	500.7	523.4	534.0	544.7	562.4	574.8	582.2	584.4	582.2
147.5°	449.3	469.1	488.9	507.3	515.4	523.4	538.9	549.1	554.3	555.7	554.3
150°	443.4	461.0	477.2	492.6	499.2	505.8	516.8	525.6	530.1	530.8	530.1
152.5°	438.3	453.0	467.6	480.1	485.6	491.1	499.2	506.6	509.5	509.5	509.5
155°	431.7	445.6	457.4	468.4	472.4	476.5	484.5	489.7	492.6	491.1	492.6
157.5°	425.8	436.8	447.1	456.6	459.9	463.2	469.1	473.5	475.0	475.0	475.0
160°	419.2	428.7	436.8	444.9	447.4	450.0	455.2	458.8	459.6	459.6	459.6
162.5°	413.3	420.7	427.3	433.9	435.7	437.5	442.7	444.9	445.6	444.9	445.6
165°	406.7	412.6	417.7	422.9	424.4	425.8	428.7	431.7	431.7	430.9	431.7
167.5°	400.1	404.5	408.9	412.6	414.0	415.5	417.0	418.5	418.5	417.7	418.5
170°	395.0	398.6	400.8	403.8	404.5	405.2	406.0	408.2	407.4	406.0	407.4
172.5°	389.8	392.0	393.5	395.7	396.0	396.4	397.2	397.9	397.2	396.4	397.2
175°	385.4	387.6	388.4	389.1	389.5	389.8	389.8	390.6	389.8	388.4	389.8
177.5°	382.5	384.0	384.0	384.7	384.7	384.7	384.7	384.7	384.0	382.5	384.0
180°	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8

TEST NUMBER: P1010064

CATALOG NUMBER: S122RDIP-B485D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9
2.5°	1084.6	1079.6	1078.2	1079.6	1078.2	1078.9	1073.9	1055.3	1060.3	1052.5	1056.7
5°	1146.1	1141.8	1132.5	1131.1	1129.7	1128.2	1121.1	1104.6	1098.2	1087.5	1086.8
7.5°	1204.7	1204.7	1197.6	1192.6	1186.2	1181.2	1171.9	1147.5	1137.5	1124.7	1117.5
10°	1262.7	1244.1	1251.9	1246.9	1231.2	1228.3	1211.2	1196.9	1177.6	1164.7	1153.3
12.5°	1304.1	1298.4	1291.3	1287.0	1282.7	1273.4	1261.9	1225.5	1215.5	1189.7	1176.9
15°	1302.7	1299.1	1301.3	1301.3	1299.8	1297.7	1288.4	1261.9	1244.8	1219.8	1197.6
17.5°	1232.6	1241.9	1251.2	1257.7	1272.0	1278.4	1287.0	1271.2	1260.5	1239.1	1215.5
20°	1110.4	1133.2	1160.4	1166.1	1179.0	1216.9	1234.1	1247.6	1251.9	1244.8	1225.5
22.5°	940.2	959.5	1025.3	1023.9	1042.4	1087.5	1137.5	1178.3	1210.5	1228.3	1221.2
25°	736.4	763.6	798.6	825.1	885.9	953.1	1015.3	1080.3	1136.1	1185.4	1197.6
27.5°	557.0	592.7	620.6	655.6	686.4	765.7	845.8	947.4	1012.4	1106.1	1154.7
30°	450.4	466.9	494.8	511.2	526.2	587.0	677.8	777.9	892.3	1000.3	1083.9
32.5°	384.7	396.1	416.8	424.0	439.7	480.5	537.7	629.2	747.2	878.0	988.1
35°	345.3	357.5	361.8	368.2	381.1	406.8	446.1	512.6	619.2	747.2	878.7
37.5°	311.7	318.2	330.3	334.6	338.9	358.2	384.7	431.1	501.9	607.0	752.9
40°	288.1	291.7	298.1	301.7	304.6	318.2	341.8	373.2	425.4	505.5	639.9
42.5°	263.1	267.4	271.7	276.0	279.6	290.3	304.6	334.6	369.6	430.4	527.7
45°	238.8	241.7	246.7	249.5	254.5	263.1	276.0	296.7	328.2	366.8	445.4
47.5°	216.6	220.2	222.4	225.9	229.5	238.8	251.0	264.5	290.3	328.2	385.4
50°	196.6	200.9	203.8	204.5	207.3	215.9	225.9	240.9	257.4	286.7	336.8
52.5°	182.3	183.0	185.2	188.0	187.3	192.3	201.6	213.1	230.2	253.8	290.3
55°	165.9	168.0	169.5	170.2	170.2	174.5	179.5	190.2	203.8	223.1	253.8
57.5°	145.1	147.3	151.6	153.0	155.2	157.3	159.4	166.6	178.0	196.6	221.6
60°	123.7	125.1	129.4	132.3	133.7	139.4	142.3	148.0	154.4	168.0	191.6
62.5°	99.4	100.8	103.0	105.8	108.7	117.3	124.4	130.1	135.1	144.4	163.7
65°	86.5	87.2	88.7	89.4	90.1	93.7	100.1	108.0	117.3	124.4	135.8
67.5°	75.1	75.8	76.5	77.9	78.6	79.4	82.2	84.4	93.7	103.7	112.3
70°	64.3	65.8	66.5	66.5	67.2	68.6	70.1	72.9	75.8	80.8	91.5
72.5°	54.3	55.1	56.5	56.5	56.5	57.9	59.3	60.8	62.2	65.1	69.4
75°	45.0	46.5	46.5	46.5	47.2	47.2	48.6	50.0	51.5	53.6	55.1
77.5°	37.2	37.2	37.2	37.2	37.9	37.9	38.6	40.0	40.8	41.5	42.9
80°	27.9	28.6	28.6	28.6	29.3	29.3	29.3	30.7	31.5	31.5	32.9
82.5°	20.7	20.7	20.7	21.4	20.7	21.4	21.4	22.2	21.4	22.2	22.9
85°	12.9	12.9	12.9	13.6	13.6	13.6	13.6	13.6	13.6	13.6	14.3
87.5°	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	7.1	6.4	6.4
90°	24.2	24.2	24.2	23.8	23.5	22.0	23.5	24.2	25.0	24.2	19.8
92.5°	45.5	48.5	49.2	52.2	55.1	63.1	74.1	94.7	113.1	111.6	86.6
95°	85.2	91.0	100.6	108.6	116.7	147.6	192.3	251.8	287.8	254.7	169.6
97.5°	152.7	167.4	196.0	218.0	240.1	314.2	393.5	472.8	469.1	362.7	225.4
100°	297.3	328.9	389.8	434.2	478.7	579.2	670.3	685.7	580.0	399.4	240.8
102.5°	559.4	618.9	686.4	734.2	781.9	848.7	851.6	765.0	583.6	385.4	241.5
105°	869.2	914.7	960.3	972.4	984.5	974.9	892.0	739.3	544.0	366.3	245.2
107.5°	1066.0	1072.6	1073.3	1058.6	1044.0	972.0	848.7	685.0	507.3	356.1	253.3
110°	1120.3	1106.4	1074.8	1044.7	1014.6	920.6	789.2	634.3	482.3	353.1	263.6

TEST NUMBER: P1010064

CATALOG NUMBER: S122RDIP-B485D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1105.6	1079.9	1032.9	997.3	961.7	859.7	734.9	599.1	466.2	353.9	274.6
115°	1063.0	1029.3	977.1	939.3	901.5	805.4	692.3	571.2	455.2	356.8	285.6
117.5°	1009.4	973.5	919.9	883.9	847.9	758.4	657.1	552.1	449.3	361.2	297.3
120°	953.7	919.1	867.8	834.4	800.9	723.1	632.1	537.4	444.2	365.6	309.1
122.5°	903.7	870.0	825.2	795.8	766.4	693.8	612.3	524.9	441.2	370.7	319.4
125°	858.9	831.0	788.5	761.0	733.4	668.8	593.2	513.2	437.5	375.9	330.4
127.5°	820.8	794.3	756.9	731.2	705.5	643.8	574.1	502.2	435.3	381.0	340.6
130°	786.3	761.3	725.3	701.1	676.9	618.9	555.7	491.1	433.9	386.9	350.2
132.5°	752.5	727.5	692.3	669.9	647.5	595.4	538.1	482.3	433.1	392.8	359.7
135°	715.8	691.6	660.0	639.4	618.9	570.4	522.0	474.3	432.4	397.2	367.8
137.5°	678.3	657.1	627.0	608.6	590.3	550.6	508.8	468.4	432.4	401.6	374.4
140°	640.2	621.1	597.6	581.4	565.3	531.5	496.3	463.2	431.7	404.5	379.6
142.5°	607.1	590.3	568.2	555.4	542.5	514.6	486.0	458.1	431.7	406.7	384.0
145°	574.8	562.4	544.7	534.0	523.4	500.7	476.5	453.7	430.2	408.2	387.6
147.5°	549.1	538.9	523.4	515.4	507.3	488.9	469.1	449.3	428.0	408.9	389.8
150°	525.6	516.8	505.8	499.2	492.6	477.2	461.0	443.4	425.8	408.2	391.3
152.5°	506.6	499.2	491.1	485.6	480.1	467.6	453.0	438.3	422.1	406.7	392.0
155°	489.7	484.5	476.5	472.4	468.4	457.4	445.6	431.7	417.7	405.2	392.8
157.5°	473.5	469.1	463.2	459.9	456.6	447.1	436.8	425.8	413.3	402.3	392.8
160°	458.8	455.2	450.0	447.4	444.9	436.8	428.7	419.2	408.9	400.1	392.8
162.5°	444.9	442.7	437.5	435.7	433.9	427.3	420.7	413.3	405.2	397.9	392.0
165°	431.7	428.7	425.8	424.4	422.9	417.7	412.6	406.7	400.1	395.0	390.6
167.5°	418.5	417.0	415.5	414.0	412.6	408.9	404.5	400.1	395.7	392.0	389.8
170°	408.2	406.0	405.2	404.5	403.8	400.8	398.6	395.0	392.0	389.8	388.4
172.5°	397.9	397.2	396.4	396.0	395.7	393.5	392.0	389.8	387.6	386.9	386.2
175°	390.6	389.8	389.8	389.5	389.1	388.4	387.6	385.4	384.7	384.0	384.7
177.5°	384.7	384.7	384.7	384.7	384.7	384.0	384.0	382.5	381.8	382.5	384.0
180°	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8

TEST NUMBER: P1010064

CATALOG NUMBER: S122RDIP-B485D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9
2.5°	1050.3	1046.7	1046.7	1044.6	1044.6	1033.2	1033.2	1036.7	1032.4	1027.4	1020.3
5°	1077.5	1069.6	1067.5	1064.6	1055.3	1041.0	1035.3	1033.2	1024.6	1013.8	1001.7
7.5°	1103.2	1090.3	1083.9	1077.5	1065.3	1045.3	1033.9	1026.0	1013.1	996.7	981.0
10°	1128.2	1111.8	1095.4	1087.5	1070.3	1045.3	1028.9	1016.0	997.4	975.2	953.1
12.5°	1151.1	1116.8	1113.9	1098.2	1073.2	1044.6	1019.6	1001.0	977.4	951.6	925.9
15°	1171.1	1136.1	1118.9	1104.6	1071.8	1036.0	1009.6	986.7	955.2	925.9	894.4
17.5°	1181.2	1143.3	1131.8	1108.2	1074.6	1028.1	992.4	964.5	930.2	895.2	859.4
20°	1191.2	1146.8	1128.2	1111.8	1066.0	1013.1	973.1	940.9	903.0	861.6	822.2
22.5°	1196.2	1146.8	1124.7	1101.8	1057.5	996.7	949.5	911.6	867.3	825.1	777.9
25°	1187.6	1142.5	1116.1	1092.5	1042.4	976.7	922.3	879.4	832.2	784.3	736.4
27.5°	1166.1	1132.5	1101.8	1077.5	1021.7	950.9	893.7	845.1	796.5	742.9	694.2
30°	1126.1	1111.1	1086.8	1059.6	998.8	928.0	860.1	810.1	756.5	702.8	652.1
32.5°	1063.9	1076.8	1061.0	1037.4	971.7	896.6	824.4	773.6	715.0	657.1	610.6
35°	988.1	1033.9	1025.3	1008.8	943.1	863.0	790.8	729.3	670.7	612.0	565.6
37.5°	905.2	974.5	981.7	971.7	910.2	828.7	749.3	689.2	629.2	569.8	522.7
40°	791.5	898.0	920.9	925.2	875.9	787.2	704.3	645.6	586.3	528.4	471.2
42.5°	687.1	821.5	850.1	868.0	832.2	746.4	662.8	597.7	539.1	486.9	429.7
45°	589.1	729.3	775.8	798.6	782.9	700.0	613.5	552.7	499.1	451.2	396.1
47.5°	488.3	629.2	694.2	730.7	730.7	652.8	566.3	506.2	454.7	414.0	365.4
50°	421.1	538.4	605.6	653.5	666.4	604.9	523.4	464.7	416.1	371.8	334.6
52.5°	358.9	464.0	519.8	569.8	607.0	553.4	475.5	422.6	374.7	333.2	303.9
55°	310.3	389.0	439.7	494.8	536.2	501.2	429.0	377.5	336.0	301.7	276.7
57.5°	263.8	332.5	373.9	422.6	466.9	440.4	382.5	338.2	301.7	271.7	249.5
60°	224.5	280.3	312.4	350.3	405.4	386.8	338.9	298.1	268.8	241.7	223.1
62.5°	190.9	235.2	262.4	289.6	339.6	331.0	293.9	262.4	237.4	214.5	198.8
65°	156.6	193.0	214.5	238.1	278.1	281.7	251.7	229.5	206.6	186.6	172.3
67.5°	126.6	155.2	174.5	194.5	226.6	236.7	215.9	197.3	178.0	161.6	148.7
70°	102.2	122.3	136.6	152.3	178.7	190.9	180.2	167.3	151.6	138.0	126.6
72.5°	80.8	93.7	102.2	114.4	135.8	148.0	147.3	135.8	124.4	115.1	105.8
75°	59.3	69.4	76.5	84.4	101.5	113.0	115.8	110.8	99.4	92.2	85.1
77.5°	45.0	50.8	54.3	60.1	72.2	82.2	86.5	85.1	77.2	71.5	66.5
80°	34.3	35.7	37.2	39.3	49.3	58.6	61.5	60.8	56.5	54.3	48.6
82.5°	24.3	25.0	25.7	26.5	30.0	37.9	40.8	42.2	38.6	36.5	31.5
85°	14.3	15.0	15.0	16.4	17.2	19.3	24.3	24.3	23.6	20.7	20.0
87.5°	7.1	7.1	6.4	6.4	7.1	7.9	9.3	10.7	9.3	8.6	7.9
90°	14.7	11.0	9.9	8.8	7.3	5.9	2.9	0.7	2.9	5.9	7.3
92.5°	58.7	38.9	34.8	30.8	25.0	21.3	15.4	11.0	15.4	21.3	25.0
95°	105.7	71.9	63.1	54.3	42.6	36.0	28.6	25.7	28.6	36.0	42.6
97.5°	136.6	93.2	83.3	73.4	60.2	50.7	42.6	38.2	42.6	50.7	60.2
100°	151.2	112.3	102.0	91.8	77.1	65.3	58.7	56.5	58.7	65.3	77.1
102.5°	164.4	129.2	119.0	108.7	93.2	81.5	74.9	73.4	74.9	81.5	93.2
105°	179.9	145.4	135.1	124.8	108.7	97.6	92.5	89.6	92.5	97.6	108.7
107.5°	195.3	161.5	151.2	141.0	124.8	114.5	109.4	107.2	109.4	114.5	124.8
110°	210.7	178.4	167.8	157.1	141.7	132.1	127.7	124.8	127.7	132.1	141.7

TEST NUMBER: P1010064

CATALOG NUMBER: S122RDIP-B485D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	225.4	194.5	183.5	172.5	157.8	149.0	143.9	141.0	143.9	149.0	157.8
115°	240.8	209.2	199.3	189.4	174.7	165.9	161.5	157.8	161.5	165.9	174.7
117.5°	254.7	225.4	215.1	204.8	190.9	182.8	178.4	175.5	178.4	182.8	190.9
120°	269.4	240.8	230.5	220.2	205.6	199.0	194.5	191.6	194.5	199.0	205.6
122.5°	283.4	256.9	246.3	235.7	221.0	213.6	209.2	207.0	209.2	213.6	221.0
125°	297.3	270.9	260.6	250.3	235.7	226.9	222.4	220.2	222.4	226.9	235.7
127.5°	310.5	284.8	274.2	263.6	249.6	240.1	234.2	231.3	234.2	240.1	249.6
130°	322.3	296.6	286.3	276.0	261.4	251.1	243.7	240.8	243.7	251.1	261.4
132.5°	332.6	308.3	298.0	287.8	272.4	261.4	253.3	249.6	253.3	261.4	272.4
135°	342.1	318.6	308.4	298.1	281.2	270.2	261.4	258.4	261.4	270.2	281.2
137.5°	350.2	326.7	317.2	307.6	290.7	279.0	270.2	266.5	270.2	279.0	290.7
140°	356.8	334.8	325.2	315.7	299.5	287.8	279.0	276.0	279.0	287.8	299.5
142.5°	361.9	340.6	331.8	323.0	307.6	295.9	287.8	285.6	287.8	295.9	307.6
145°	367.1	347.2	339.2	331.1	316.4	305.4	298.1	295.1	298.1	305.4	316.4
147.5°	371.5	352.4	345.0	337.7	325.2	314.9	307.6	305.4	307.6	314.9	325.2
150°	374.4	357.5	350.9	344.3	333.3	323.8	317.9	315.7	317.9	323.8	333.3
152.5°	377.3	362.7	356.8	350.9	340.6	332.6	326.7	326.0	326.7	332.6	340.6
155°	380.3	367.8	362.3	356.8	348.7	340.6	336.2	335.5	336.2	340.6	348.7
157.5°	382.5	371.5	366.7	361.9	355.3	348.0	344.3	343.6	344.3	348.0	355.3
160°	384.0	375.1	371.1	367.1	361.2	355.3	352.4	351.7	352.4	355.3	361.2
162.5°	384.7	377.3	374.4	371.5	366.3	361.9	359.0	359.7	359.0	361.9	366.3
165°	385.4	378.8	376.6	374.4	370.7	366.3	364.9	365.6	364.9	366.3	370.7
167.5°	385.4	380.3	378.8	377.3	374.4	371.5	370.0	370.7	370.0	371.5	374.4
170°	384.7	381.0	379.9	378.8	377.3	375.1	374.4	375.9	374.4	375.1	377.3
172.5°	384.0	381.8	381.0	380.3	379.6	377.3	378.1	378.8	378.1	377.3	379.6
175°	383.2	381.8	381.4	381.0	381.0	379.6	380.3	381.0	380.3	379.6	381.0
177.5°	382.5	381.8	381.8	381.8	381.8	380.3	381.0	382.5	381.0	380.3	381.8
180°	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8

TEST NUMBER: P1010064

CATALOG NUMBER: S122RDIP-B485D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9
2.5°	1017.4	1018.1	1020.3	1013.8	1003.8	999.5	986.7	984.5	982.4	982.4	984.5
5°	994.5	991.7	992.4	980.2	965.9	957.4	939.5	942.3	933.1	927.3	928.8
7.5°	969.5	961.7	960.9	945.2	927.3	911.6	893.0	888.7	880.1	870.1	865.8
10°	938.1	932.3	921.6	903.7	880.9	868.0	843.0	828.0	825.8	810.8	805.1
12.5°	905.9	895.9	885.1	860.1	834.4	813.7	795.1	778.6	767.2	754.3	745.7
15°	868.7	856.6	844.4	817.9	787.9	767.2	739.3	715.0	681.4	654.9	639.9
17.5°	828.0	814.4	797.9	768.6	739.3	710.7	659.2	630.6	607.0	591.3	582.0
20°	785.8	770.8	754.3	725.0	674.2	624.2	595.6	573.4	559.1	543.4	531.9
22.5°	741.4	725.7	707.8	662.1	608.5	573.4	551.3	530.5	509.8	501.2	495.5
25°	700.0	685.7	662.8	600.6	558.4	526.2	501.2	487.6	476.9	465.5	454.7
27.5°	657.1	630.6	598.4	546.2	519.8	486.9	469.0	459.0	440.4	432.6	427.6
30°	605.6	576.3	545.5	508.4	477.6	454.7	438.3	421.8	411.1	403.3	394.7
32.5°	553.4	525.5	506.2	467.6	444.7	421.1	405.4	395.4	379.7	374.7	371.1
35°	508.4	484.8	467.6	436.1	414.7	393.2	381.8	366.8	356.8	347.5	341.8
37.5°	464.0	451.2	433.3	406.8	383.9	366.8	351.1	346.1	332.5	327.5	321.7
40°	433.3	414.0	399.0	376.1	356.8	338.2	328.2	316.7	307.4	299.6	297.4
42.5°	396.1	381.8	373.2	348.2	328.2	317.5	305.3	292.4	285.3	278.8	271.0
45°	368.2	355.3	343.2	323.2	305.3	291.7	281.0	272.4	260.3	257.4	245.2
47.5°	338.9	326.0	316.7	296.7	280.3	267.4	259.5	248.1	238.1	231.7	225.9
50°	309.6	298.9	290.3	273.1	258.8	245.2	234.5	223.1	218.8	208.1	204.5
52.5°	281.7	274.6	265.3	248.8	234.5	223.1	211.6	202.3	195.9	190.2	185.9
55°	258.1	246.7	242.4	224.5	212.4	200.2	190.2	184.5	176.6	173.0	169.5
57.5°	231.7	225.2	218.1	204.5	190.9	179.5	172.3	163.7	159.4	155.2	152.3
60°	208.8	199.5	193.8	182.3	170.2	159.4	153.0	146.6	140.9	137.3	131.6
62.5°	182.3	175.2	171.6	159.4	149.4	139.4	133.7	127.3	123.0	116.5	109.4
65°	159.4	153.7	149.4	139.4	130.1	120.8	115.1	107.2	101.5	98.0	97.2
67.5°	139.4	135.1	128.7	119.4	110.1	103.0	96.5	90.1	89.4	87.9	87.9
70°	117.3	113.0	109.4	99.4	91.5	83.7	82.2	80.1	77.9	77.2	75.8
72.5°	98.0	94.4	90.1	81.5	73.6	71.5	70.1	68.6	66.5	65.8	65.1
75°	79.4	74.4	71.5	63.6	61.5	60.1	58.6	56.5	55.1	54.3	52.9
77.5°	60.8	55.8	55.8	51.5	50.0	47.9	46.5	45.0	44.3	42.9	42.9
80°	42.9	42.9	41.5	39.3	37.2	36.5	34.3	33.6	32.9	33.6	32.2
82.5°	31.5	28.6	28.6	27.2	25.7	25.0	23.6	23.6	22.9	22.9	22.9
85°	17.9	17.9	17.2	15.7	15.0	15.0	14.3	14.3	13.6	13.6	12.9
87.5°	7.1	6.4	7.1	6.4	6.4	5.7	5.7	5.7	5.0	5.7	5.0
90°	8.8	9.9	11.0	14.7	19.8	24.2	25.0	24.2	23.5	22.0	23.5
92.5°	30.8	34.8	38.9	58.7	86.6	111.6	113.1	94.7	74.1	63.1	55.1
95°	54.3	63.1	71.9	105.7	169.6	254.7	287.8	251.8	192.3	147.6	116.7
97.5°	73.4	83.3	93.2	136.6	225.4	362.7	469.1	472.8	393.5	314.2	240.1
100°	91.8	102.0	112.3	151.2	240.8	399.4	580.0	685.7	670.3	579.2	478.7
102.5°	108.7	119.0	129.2	164.4	241.5	385.4	583.6	765.0	851.6	848.7	781.9
105°	124.8	135.1	145.4	179.9	245.2	366.3	544.0	739.3	892.0	974.9	984.5
107.5°	141.0	151.2	161.5	195.3	253.3	356.1	507.3	685.0	848.7	972.0	1044.0
110°	157.1	167.8	178.4	210.7	263.6	353.1	482.3	634.3	789.2	920.6	1014.6

TEST NUMBER: P1010064

CATALOG NUMBER: S122RDIP-B485D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	172.5	183.5	194.5	225.4	274.6	353.9	466.2	599.1	734.9	859.7	961.7
115°	189.4	199.3	209.2	240.8	285.6	356.8	455.2	571.2	692.3	805.4	901.5
117.5°	204.8	215.1	225.4	254.7	297.3	361.2	449.3	552.1	657.1	758.4	847.9
120°	220.2	230.5	240.8	269.4	309.1	365.6	444.2	537.4	632.1	723.1	800.9
122.5°	235.7	246.3	256.9	283.4	319.4	370.7	441.2	524.9	612.3	693.8	766.4
125°	250.3	260.6	270.9	297.3	330.4	375.9	437.5	513.2	593.2	668.8	733.4
127.5°	263.6	274.2	284.8	310.5	340.6	381.0	435.3	502.2	574.1	643.8	705.5
130°	276.0	286.3	296.6	322.3	350.2	386.9	433.9	491.1	555.7	618.9	676.9
132.5°	287.8	298.0	308.3	332.6	359.7	392.8	433.1	482.3	538.1	595.4	647.5
135°	298.1	308.4	318.6	342.1	367.8	397.2	432.4	474.3	522.0	570.4	618.9
137.5°	307.6	317.2	326.7	350.2	374.4	401.6	432.4	468.4	508.8	550.6	590.3
140°	315.7	325.2	334.8	356.8	379.6	404.5	431.7	463.2	496.3	531.5	565.3
142.5°	323.0	331.8	340.6	361.9	384.0	406.7	431.7	458.1	486.0	514.6	542.5
145°	331.1	339.2	347.2	367.1	387.6	408.2	430.2	453.7	476.5	500.7	523.4
147.5°	337.7	345.0	352.4	371.5	389.8	408.9	428.0	449.3	469.1	488.9	507.3
150°	344.3	350.9	357.5	374.4	391.3	408.2	425.8	443.4	461.0	477.2	492.6
152.5°	350.9	356.8	362.7	377.3	392.0	406.7	422.1	438.3	453.0	467.6	480.1
155°	356.8	362.3	367.8	380.3	392.8	405.2	417.7	431.7	445.6	457.4	468.4
157.5°	361.9	366.7	371.5	382.5	392.8	402.3	413.3	425.8	436.8	447.1	456.6
160°	367.1	371.1	375.1	384.0	392.8	400.1	408.9	419.2	428.7	436.8	444.9
162.5°	371.5	374.4	377.3	384.7	392.0	397.9	405.2	413.3	420.7	427.3	433.9
165°	374.4	376.6	378.8	385.4	390.6	395.0	400.1	406.7	412.6	417.7	422.9
167.5°	377.3	378.8	380.3	385.4	389.8	392.0	395.7	400.1	404.5	408.9	412.6
170°	378.8	379.9	381.0	384.7	388.4	389.8	392.0	395.0	398.6	400.8	403.8
172.5°	380.3	381.0	381.8	384.0	386.2	386.9	387.6	389.8	392.0	393.5	395.7
175°	381.0	381.4	381.8	383.2	384.7	384.0	384.7	385.4	387.6	388.4	389.1
177.5°	381.8	381.8	381.8	382.5	384.0	382.5	381.8	382.5	384.0	384.0	384.7
180°	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8

TEST NUMBER: P1010064

CATALOG NUMBER: S122RDIP-B485D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9
2.5°	984.5	983.1	978.8	980.2	978.1	978.1	976.7	976.7	976.7	980.2	978.1
5°	930.9	925.9	920.9	918.8	916.6	914.5	914.5	913.7	920.2	918.8	924.5
7.5°	864.4	863.0	853.0	853.0	849.4	848.0	851.5	852.3	853.0	854.4	858.0
10°	805.1	801.5	787.2	788.6	786.5	783.6	785.8	784.3	789.3	790.8	789.3
12.5°	735.0	728.6	712.8	705.0	696.4	690.0	697.8	692.1	712.1	717.8	733.6
15°	642.1	629.9	619.2	619.2	611.3	605.6	609.2	615.6	619.9	626.3	629.2
17.5°	579.9	574.8	566.3	561.3	559.1	557.0	557.0	559.8	569.1	568.4	574.1
20°	526.9	524.1	519.8	513.4	511.2	509.8	509.8	509.8	516.2	521.9	525.5
22.5°	490.5	488.3	485.5	476.9	472.6	471.2	474.7	476.9	481.9	486.2	489.8
25°	454.0	449.0	444.0	441.1	439.0	439.0	440.4	441.1	443.3	445.4	449.7
27.5°	424.0	420.4	413.3	405.4	405.4	403.3	404.7	406.1	411.1	418.3	421.8
30°	390.4	389.7	386.8	383.9	381.1	379.7	382.5	384.7	385.4	389.0	389.0
32.5°	366.1	361.1	356.1	353.2	351.8	351.1	351.8	354.6	354.6	358.9	363.9
35°	341.8	338.9	333.9	328.9	327.5	323.9	326.7	329.6	334.6	336.8	338.9
37.5°	315.3	311.7	309.6	308.2	305.3	306.0	303.9	308.2	312.4	311.7	313.2
40°	295.3	288.9	282.4	281.7	281.0	280.3	280.3	281.0	283.8	286.7	291.0
42.5°	269.5	267.4	261.7	256.0	254.5	253.1	251.7	254.5	260.3	265.3	267.4
45°	243.1	240.2	238.8	234.5	231.7	230.9	229.5	233.1	238.1	240.2	241.7
47.5°	218.8	218.1	213.8	214.5	212.4	213.1	212.4	214.5	214.5	216.6	218.1
50°	202.3	200.2	198.1	196.6	194.5	194.5	193.8	194.5	197.3	200.2	199.5
52.5°	185.9	182.3	181.6	180.9	179.5	180.9	178.7	179.5	182.3	183.8	183.0
55°	166.6	165.9	164.4	163.0	162.3	161.6	161.6	161.6	164.4	166.6	167.3
57.5°	151.6	148.0	145.1	145.1	142.3	141.6	143.0	143.7	145.9	147.3	148.7
60°	130.8	129.4	125.1	123.0	118.7	118.0	118.0	120.8	124.4	129.4	130.8
62.5°	108.7	106.5	105.8	105.8	105.8	105.8	105.8	105.8	105.8	106.5	106.5
65°	96.5	97.2	96.5	95.8	96.5	96.5	95.8	95.8	95.8	96.5	97.2
67.5°	86.5	85.8	86.5	85.8	85.1	85.1	84.4	85.1	85.8	86.5	86.5
70°	75.1	75.1	74.4	75.1	74.4	73.6	72.9	72.9	74.4	75.1	75.1
72.5°	64.3	64.3	63.6	63.6	62.2	62.2	62.9	62.2	62.2	64.3	64.3
75°	53.6	52.9	52.2	52.2	51.5	51.5	51.5	50.8	52.2	52.2	52.9
77.5°	42.2	42.2	42.2	41.5	41.5	40.8	40.8	41.5	41.5	41.5	42.2
80°	32.2	32.2	32.2	31.5	30.7	30.7	30.7	30.7	30.7	31.5	30.7
82.5°	22.2	22.2	22.2	22.2	22.2	21.4	21.4	21.4	22.2	22.2	21.4
85°	13.6	12.9	13.6	13.6	12.9	13.6	12.9	12.9	12.2	12.2	12.9
87.5°	5.7	5.0	4.3	4.3	5.0	4.3	4.3	4.3	5.0	4.3	4.3
90°	23.8	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	23.8
92.5°	52.2	49.2	48.5	45.5	46.3	44.8	46.3	45.5	48.5	49.2	52.2
95°	108.6	100.6	91.0	85.2	83.0	83.7	83.0	85.2	91.0	100.6	108.6
97.5°	218.0	196.0	167.4	152.7	144.6	140.2	144.6	152.7	167.4	196.0	218.0
100°	434.2	389.8	328.9	297.3	276.0	262.8	276.0	297.3	328.9	389.8	434.2
102.5°	734.2	686.4	618.9	559.4	531.5	512.4	531.5	559.4	618.9	686.4	734.2
105°	972.4	960.3	914.7	869.2	837.7	827.4	837.7	869.2	914.7	960.3	972.4
107.5°	1058.6	1073.3	1072.6	1066.0	1056.4	1039.5	1056.4	1066.0	1072.6	1073.3	1058.6
110°	1044.7	1074.8	1106.4	1120.3	1126.9	1126.2	1126.9	1120.3	1106.4	1074.8	1044.7

TEST NUMBER: P1010064

CATALOG NUMBER: S122RDIP-B485D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	997.3	1032.9	1079.9	1105.6	1119.6	1124.7	1119.6	1105.6	1079.9	1032.9	997.3
115°	939.3	977.1	1029.3	1063.0	1082.1	1088.7	1082.1	1063.0	1029.3	977.1	939.3
117.5°	883.9	919.9	973.5	1009.4	1029.3	1034.4	1029.3	1009.4	973.5	919.9	883.9
120°	834.4	867.8	919.1	953.7	974.9	982.3	974.9	953.7	919.1	867.8	834.4
122.5°	795.8	825.2	870.0	903.7	922.1	928.0	922.1	903.7	870.0	825.2	795.8
125°	761.0	788.5	831.0	858.9	877.3	883.2	877.3	858.9	831.0	788.5	761.0
127.5°	731.2	756.9	794.3	820.8	836.9	841.3	836.9	820.8	794.3	756.9	731.2
130°	701.1	725.3	761.3	786.3	800.9	806.8	800.9	786.3	761.3	725.3	701.1
132.5°	669.9	692.3	727.5	752.5	765.7	770.8	765.7	752.5	727.5	692.3	669.9
135°	639.4	660.0	691.6	715.8	729.0	731.9	729.0	715.8	691.6	660.0	639.4
137.5°	608.6	627.0	657.1	678.3	690.1	694.5	690.1	678.3	657.1	627.0	608.6
140°	581.4	597.6	621.1	640.2	651.2	655.6	651.2	640.2	621.1	597.6	581.4
142.5°	555.4	568.2	590.3	607.1	616.7	616.7	616.7	607.1	590.3	568.2	555.4
145°	534.0	544.7	562.4	574.8	582.2	584.4	582.2	574.8	562.4	544.7	534.0
147.5°	515.4	523.4	538.9	549.1	554.3	555.7	554.3	549.1	538.9	523.4	515.4
150°	499.2	505.8	516.8	525.6	530.1	530.8	530.1	525.6	516.8	505.8	499.2
152.5°	485.6	491.1	499.2	506.6	509.5	509.5	509.5	506.6	499.2	491.1	485.6
155°	472.4	476.5	484.5	489.7	492.6	491.1	492.6	489.7	484.5	476.5	472.4
157.5°	459.9	463.2	469.1	473.5	475.0	475.0	475.0	473.5	469.1	463.2	459.9
160°	447.4	450.0	455.2	458.8	459.6	459.6	459.6	458.8	455.2	450.0	447.4
162.5°	435.7	437.5	442.7	444.9	445.6	444.9	445.6	444.9	442.7	437.5	435.7
165°	424.4	425.8	428.7	431.7	431.7	430.9	431.7	431.7	428.7	425.8	424.4
167.5°	414.0	415.5	417.0	418.5	418.5	417.7	418.5	418.5	417.0	415.5	414.0
170°	404.5	405.2	406.0	408.2	407.4	406.0	407.4	408.2	406.0	405.2	404.5
172.5°	396.0	396.4	397.2	397.9	397.2	396.4	397.2	397.9	397.2	396.4	396.0
175°	389.5	389.8	389.8	390.6	389.8	388.4	389.8	390.6	389.8	389.8	389.5
177.5°	384.7	384.7	384.7	384.7	384.0	382.5	384.0	384.7	384.7	384.7	384.7
180°	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8

TEST NUMBER: P1010064

CATALOG NUMBER: S122RDIP-B485D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9	1028.9
2.5°	980.2	983.8	982.4	974.5	982.4	984.5	988.8	993.1	996.0	1000.3	1003.8
5°	918.8	925.9	930.2	925.9	940.2	942.3	952.4	958.1	966.7	973.8	979.5
7.5°	860.8	866.6	875.1	876.6	885.1	895.2	909.5	923.8	937.3	944.5	950.9
10°	798.6	808.6	821.5	818.7	831.5	847.3	862.3	885.1	896.6	909.5	920.9
12.5°	736.4	742.9	760.0	765.7	784.3	796.5	817.2	831.5	860.1	875.1	885.1
15°	627.8	654.2	675.7	701.4	725.7	748.6	767.2	792.9	817.9	829.4	845.8
17.5°	578.4	590.6	603.4	616.3	647.8	688.5	721.4	749.3	770.8	785.8	805.1
20°	526.9	539.1	553.4	565.6	584.9	614.2	654.9	702.8	728.6	744.3	762.9
22.5°	490.5	501.9	511.2	521.9	537.0	558.4	589.1	648.5	682.8	702.1	718.6
25°	451.2	465.5	475.5	483.3	495.5	519.1	544.1	577.7	639.2	654.2	677.1
27.5°	424.0	428.3	439.7	451.9	464.0	476.9	502.6	531.2	572.7	605.6	633.5
30°	391.8	402.5	413.3	418.3	429.0	447.6	463.3	494.1	526.2	552.0	585.6
32.5°	367.5	373.9	381.1	393.2	403.3	416.1	431.9	457.6	484.8	501.2	526.9
35°	340.3	344.6	359.6	364.6	374.7	387.5	403.3	423.3	452.6	465.5	484.0
37.5°	314.6	324.6	328.9	340.3	349.6	362.5	373.9	396.8	416.1	431.1	448.3
40°	294.6	298.9	306.7	316.7	324.6	334.6	348.9	365.4	386.1	398.2	413.3
42.5°	270.3	273.8	283.8	289.6	302.4	311.7	320.3	340.3	358.9	368.2	383.2
45°	243.8	252.4	258.8	270.3	277.4	288.9	299.6	313.9	331.0	341.8	350.3
47.5°	220.9	229.5	235.9	246.7	258.1	263.1	274.6	289.6	305.3	313.9	326.0
50°	202.3	205.2	217.4	222.4	234.5	244.5	252.4	265.3	282.4	287.4	297.4
52.5°	184.5	186.6	194.5	200.9	211.6	220.2	230.2	242.4	256.7	264.5	272.4
55°	168.7	170.2	173.7	180.9	188.0	198.8	208.1	219.5	231.7	240.2	247.4
57.5°	150.9	153.7	156.6	160.9	168.0	178.0	188.0	198.8	208.8	214.5	223.8
60°	130.1	134.4	139.4	144.4	149.4	156.6	168.0	178.0	187.3	192.3	199.5
62.5°	108.0	116.5	120.8	126.6	130.8	137.3	145.9	157.3	163.7	170.2	175.9
65°	97.2	98.0	98.7	104.4	112.3	118.7	126.6	135.1	145.1	149.4	153.7
67.5°	86.5	87.2	88.7	89.4	92.2	99.4	108.0	117.3	125.1	128.0	132.3
70°	75.8	75.8	78.6	79.4	80.1	80.8	87.9	97.2	104.4	108.0	113.0
72.5°	64.3	65.1	66.5	67.2	68.6	70.1	72.2	77.2	85.8	89.4	95.1
75°	52.9	53.6	54.3	55.1	57.2	57.9	60.1	62.9	66.5	70.8	74.4
77.5°	42.2	42.2	42.9	44.3	45.8	46.5	48.6	50.0	51.5	53.6	56.5
80°	31.5	32.2	32.2	33.6	33.6	34.3	35.0	37.2	38.6	40.0	41.5
82.5°	21.4	22.9	22.9	22.9	23.6	24.3	25.0	25.0	26.5	27.2	29.3
85°	12.9	13.6	13.6	13.6	12.9	14.3	14.3	15.0	15.0	15.0	15.7
87.5°	5.0	4.3	5.0	5.0	5.0	5.7	5.0	5.0	5.7	6.4	6.4
90°	23.5	22.0	23.5	24.2	25.0	24.2	19.8	14.7	11.0	9.9	8.8
92.5°	55.1	63.1	74.1	94.7	113.1	111.6	86.6	58.7	38.9	34.8	30.8
95°	116.7	147.6	192.3	251.8	287.8	254.7	169.6	105.7	71.9	63.1	54.3
97.5°	240.1	314.2	393.5	472.8	469.1	362.7	225.4	136.6	93.2	83.3	73.4
100°	478.7	579.2	670.3	685.7	580.0	399.4	240.8	151.2	112.3	102.0	91.8
102.5°	781.9	848.7	851.6	765.0	583.6	385.4	241.5	164.4	129.2	119.0	108.7
105°	984.5	974.9	892.0	739.3	544.0	366.3	245.2	179.9	145.4	135.1	124.8
107.5°	1044.0	972.0	848.7	685.0	507.3	356.1	253.3	195.3	161.5	151.2	141.0
110°	1014.6	920.6	789.2	634.3	482.3	353.1	263.6	210.7	178.4	167.8	157.1

TEST NUMBER: P1010064

CATALOG NUMBER: S122RDIP-B485D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	961.7	859.7	734.9	599.1	466.2	353.9	274.6	225.4	194.5	183.5	172.5
115°	901.5	805.4	692.3	571.2	455.2	356.8	285.6	240.8	209.2	199.3	189.4
117.5°	847.9	758.4	657.1	552.1	449.3	361.2	297.3	254.7	225.4	215.1	204.8
120°	800.9	723.1	632.1	537.4	444.2	365.6	309.1	269.4	240.8	230.5	220.2
122.5°	766.4	693.8	612.3	524.9	441.2	370.7	319.4	283.4	256.9	246.3	235.7
125°	733.4	668.8	593.2	513.2	437.5	375.9	330.4	297.3	270.9	260.6	250.3
127.5°	705.5	643.8	574.1	502.2	435.3	381.0	340.6	310.5	284.8	274.2	263.6
130°	676.9	618.9	555.7	491.1	433.9	386.9	350.2	322.3	296.6	286.3	276.0
132.5°	647.5	595.4	538.1	482.3	433.1	392.8	359.7	332.6	308.3	298.0	287.8
135°	618.9	570.4	522.0	474.3	432.4	397.2	367.8	342.1	318.6	308.4	298.1
137.5°	590.3	550.6	508.8	468.4	432.4	401.6	374.4	350.2	326.7	317.2	307.6
140°	565.3	531.5	496.3	463.2	431.7	404.5	379.6	356.8	334.8	325.2	315.7
142.5°	542.5	514.6	486.0	458.1	431.7	406.7	384.0	361.9	340.6	331.8	323.0
145°	523.4	500.7	476.5	453.7	430.2	408.2	387.6	367.1	347.2	339.2	331.1
147.5°	507.3	488.9	469.1	449.3	428.0	408.9	389.8	371.5	352.4	345.0	337.7
150°	492.6	477.2	461.0	443.4	425.8	408.2	391.3	374.4	357.5	350.9	344.3
152.5°	480.1	467.6	453.0	438.3	422.1	406.7	392.0	377.3	362.7	356.8	350.9
155°	468.4	457.4	445.6	431.7	417.7	405.2	392.8	380.3	367.8	362.3	356.8
157.5°	456.6	447.1	436.8	425.8	413.3	402.3	392.8	382.5	371.5	366.7	361.9
160°	444.9	436.8	428.7	419.2	408.9	400.1	392.8	384.0	375.1	371.1	367.1
162.5°	433.9	427.3	420.7	413.3	405.2	397.9	392.0	384.7	377.3	374.4	371.5
165°	422.9	417.7	412.6	406.7	400.1	395.0	390.6	385.4	378.8	376.6	374.4
167.5°	412.6	408.9	404.5	400.1	395.7	392.0	389.8	385.4	380.3	378.8	377.3
170°	403.8	400.8	398.6	395.0	392.0	389.8	388.4	384.7	381.0	379.9	378.8
172.5°	395.7	393.5	392.0	389.8	387.6	386.9	386.2	384.0	381.8	381.0	380.3
175°	389.1	388.4	387.6	385.4	384.7	384.0	384.7	383.2	381.8	381.4	381.0
177.5°	384.7	384.0	384.0	382.5	381.8	382.5	384.0	382.5	381.8	381.8	381.8
180°	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8	381.8

TEST NUMBER: P1010064

CATALOG NUMBER: S122RDIP-B485D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1028.9	1028.9	1028.9	1028.9
2.5°	1010.3	1008.1	1021.0	1035.3
5°	989.5	993.1	1009.6	1029.6
7.5°	968.1	976.0	995.3	1021.7
10°	938.1	952.4	981.7	1008.8
12.5°	908.7	928.0	955.9	988.1
15°	875.9	897.3	931.6	970.2
17.5°	839.4	863.7	903.7	945.9
20°	800.8	833.0	875.1	920.9
22.5°	757.9	796.5	840.1	890.9
25°	716.4	758.6	802.2	860.8
27.5°	675.7	717.1	765.7	825.1
30°	634.9	672.8	725.0	788.6
32.5°	591.3	630.6	685.7	750.7
35°	551.3	590.6	642.1	706.4
37.5°	508.4	550.5	599.9	666.4
40°	458.3	507.6	555.5	619.2
42.5°	416.8	469.0	515.5	575.6
45°	383.9	433.3	471.9	530.5
47.5°	353.2	393.2	432.6	486.9
50°	323.9	354.6	395.4	444.0
52.5°	293.9	320.3	355.3	401.1
55°	266.7	291.7	323.2	358.2
57.5°	241.7	259.5	291.0	322.5
60°	213.8	232.4	256.7	283.1
62.5°	190.2	204.5	227.4	249.5
65°	165.2	178.7	195.9	216.6
67.5°	142.3	154.4	168.0	184.5
70°	121.5	130.8	140.9	155.2
72.5°	99.4	109.4	118.7	130.1
75°	81.5	85.8	93.7	101.5
77.5°	62.9	68.6	72.9	79.4
80°	45.0	50.0	51.5	56.5
82.5°	30.0	32.9	35.7	37.2
85°	17.2	18.6	21.4	22.2
87.5°	6.4	7.1	8.6	10.0
90°	7.3	5.9	2.9	0.7
92.5°	25.0	21.3	15.4	11.0
95°	42.6	36.0	28.6	25.7
97.5°	60.2	50.7	42.6	38.2
100°	77.1	65.3	58.7	56.5
102.5°	93.2	81.5	74.9	73.4
105°	108.7	97.6	92.5	89.6
107.5°	124.8	114.5	109.4	107.2
110°	141.7	132.1	127.7	124.8



TEST NUMBER: P1010064

CATALOG NUMBER: S122RDIP-B485D725UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	157.8	149.0	143.9	141.0
115°	174.7	165.9	161.5	157.8
117.5°	190.9	182.8	178.4	175.5
120°	205.6	199.0	194.5	191.6
122.5°	221.0	213.6	209.2	207.0
125°	235.7	226.9	222.4	220.2
127.5°	249.6	240.1	234.2	231.3
130°	261.4	251.1	243.7	240.8
132.5°	272.4	261.4	253.3	249.6
135°	281.2	270.2	261.4	258.4
137.5°	290.7	279.0	270.2	266.5
140°	299.5	287.8	279.0	276.0
142.5°	307.6	295.9	287.8	285.6
145°	316.4	305.4	298.1	295.1
147.5°	325.2	314.9	307.6	305.4
150°	333.3	323.8	317.9	315.7
152.5°	340.6	332.6	326.7	326.0
155°	348.7	340.6	336.2	335.5
157.5°	355.3	348.0	344.3	343.6
160°	361.2	355.3	352.4	351.7
162.5°	366.3	361.9	359.0	359.7
165°	370.7	366.3	364.9	365.6
167.5°	374.4	371.5	370.0	370.7
170°	377.3	375.1	374.4	375.9
172.5°	379.6	377.3	378.1	378.8
175°	381.0	379.6	380.3	381.0
177.5°	381.8	380.3	381.0	382.5
180°	381.8	381.8	381.8	381.8

(END OF REPORT)