

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010070

Luminaire Tested: S122RDIP-B485D925UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010070
REPORT IS A COMBINATION OF REPORTS P988380 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B485D925UB27-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5385.0 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010070

CATALOG NUMBER: S122RDIP-B485D925UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1010070

CATALOG NUMBER: S122RDIP-B485D925UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42	42	42	34
1	95	91	87	84	85	82	79	76	66	64	62	51	50	49	37	37	36	36	36	30
2	87	80	74	69	78	72	68	64	58	55	52	46	43	41	34	32	31	31	31	26
3	79	71	64	58	72	64	58	54	52	48	45	41	38	36	30	29	27	27	27	23
4	73	63	55	50	66	57	51	46	47	42	38	37	34	31	28	26	24	24	24	20
5	67	56	49	43	61	51	45	40	42	37	33	33	30	27	25	23	21	21	21	18
6	62	51	43	38	56	46	40	35	38	33	29	30	27	24	23	21	19	19	19	16
7	57	46	38	33	52	42	35	31	35	30	26	28	24	22	21	19	17	17	17	14
8	53	42	34	29	48	38	32	27	32	27	23	25	22	19	20	17	16	16	16	13
9	50	38	31	26	45	35	29	25	29	24	21	23	20	18	18	16	14	14	14	12
10	46	35	28	24	42	32	26	22	27	22	19	22	18	16	17	15	13	13	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16800	16800	16800	16800
5°	16838	17843	16897	14255
10°	16653	18861	16771	11771
15°	16292	18866	16568	8843
20°	15857	15595	16202	7295
25°	15331	9745	15661	6206
30°	14658	6240	15056	5343
35°	13839	4794	14287	4573
40°	12927	4030	13479	4000
45°	11951	3431	12451	3357
50°	10952	2914	11464	2904
55°	9846	2533	10376	2500
60°	8864	1932	9331	1908
65°	7945	1454	8415	1650
70°	6929	1161	7475	1344
75°	5857	890	6394	1016
80°	4655	605	5006	666
85°	3235	313	3546	329

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 15368 cd/sqm

TEST NUMBER: P1010070

CATALOG NUMBER: S122RDIP-B485D925UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.7	1.9
10°-20°	281.0	5.2
20°-30°	361.6	6.7
30°-40°	343.1	6.4
40°-50°	294.0	5.5
50°-60°	223.9	4.2
60°-70°	141.2	2.6
70°-80°	70.5	1.3
80°-90°	21.4	0.4
90°-100°	198.6	3.7
100°-110°	699.4	13.0
110°-120°	734.5	13.6
120°-130°	604.3	11.2
130°-140°	485.4	9.0
140°-150°	366.7	6.8
150°-160°	257.8	4.8
160°-170°	151.7	2.8
170°-180°	49.4	0.9
0°-30°	743.3	13.8
0°-40°	1086.3	20.2
0°-60°	1604.3	29.8
0°-90°	1837.3	34.1
90°-120°	1632.5	30.3
90°-150°	3088.8	57.4
90°-180°	3548.0	65.9
0°-180°	5385.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1061	1061	1061	1061	1061	
5°	1062	1181	1066	943	1062	101
15°	1001	1333	1018	625	1001	282
25°	888	711	907	453	888	408
35°	729	350	752	334	729	456
45°	547	243	570	238	547	422
55°	370	169	389	167	370	333
65°	224	88	237	100	224	222
75°	105	46	114	53	105	113
85°	23	13	25	14	23	26
90°	1	32	1	32	1	4
95°	34	112	34	112	34	35
105°	120	1104	120	1104	120	127
115°	211	1453	211	1453	211	209
125°	294	1179	294	1179	294	261
135°	345	977	345	977	345	266
145°	394	780	394	780	394	247
155°	448	655	448	655	448	206
165°	488	575	488	575	488	138
175°	508	518	508	518	508	48
180°	509	509	509	509	509	

TEST NUMBER: P1010070

CATALOG NUMBER: S122RDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1067.9	1072.3	1074.5	1077.5	1084.1	1088.6	1095.2	1096.7	1095.9	1098.9	1090.8
5°	1062.0	1071.6	1080.4	1087.8	1099.6	1107.0	1115.1	1124.7	1126.9	1138.0	1131.3
7.5°	1053.9	1067.9	1080.4	1095.2	1112.9	1122.5	1135.0	1149.8	1156.4	1169.7	1173.4
10°	1040.6	1060.5	1081.9	1097.4	1121.7	1138.7	1150.5	1174.1	1189.6	1209.5	1206.6
12.5°	1019.2	1045.0	1073.8	1099.6	1131.3	1142.4	1164.5	1188.9	1208.8	1227.2	1243.4
15°	1000.8	1030.3	1062.0	1093.7	1129.9	1150.5	1172.6	1204.3	1225.7	1258.2	1272.2
17.5°	975.7	1013.3	1050.9	1086.3	1129.1	1152.7	1180.0	1211.0	1242.7	1273.7	1284.7
20°	949.9	990.5	1031.0	1079.0	1127.6	1150.5	1178.5	1216.9	1247.9	1272.2	1272.2
22.5°	918.9	968.3	1014.8	1060.5	1113.6	1146.8	1175.6	1220.6	1242.7	1247.9	1227.9
25°	888.0	937.4	988.3	1045.0	1105.5	1135.0	1167.5	1209.5	1216.9	1196.2	1144.6
27.5°	851.1	906.4	963.9	1025.1	1088.6	1125.4	1154.9	1183.0	1168.9	1113.6	1033.2
30°	813.5	873.2	938.1	996.4	1073.1	1107.0	1132.1	1140.2	1095.9	1006.0	902.0
32.5°	774.4	832.6	901.2	971.3	1048.7	1081.2	1097.4	1076.0	994.9	881.3	754.5
35°	728.7	794.3	865.8	938.8	1015.5	1039.9	1049.5	997.1	893.1	746.4	620.2
37.5°	687.4	753.0	829.7	904.2	978.7	991.9	982.4	900.5	768.5	623.2	500.0
40°	638.7	708.7	784.0	867.3	928.5	932.2	908.6	802.4	638.7	502.2	426.3
42.5°	593.7	664.5	739.7	824.5	871.0	858.5	826.7	687.4	533.2	432.9	371.7
45°	547.2	614.3	695.5	770.7	803.9	774.4	726.4	578.2	447.7	372.4	325.2
47.5°	502.2	564.9	645.3	717.6	723.5	690.3	633.5	484.5	387.9	327.5	289.1
50°	458.0	520.7	595.9	655.6	649.7	604.0	539.9	421.1	337.0	289.1	257.4
52.5°	413.7	470.5	543.5	590.7	565.7	521.4	458.0	357.0	294.3	252.2	227.9
55°	369.5	422.6	485.3	524.4	484.5	433.7	388.7	306.1	255.2	221.3	202.8
57.5°	332.6	374.7	432.2	455.8	407.8	368.0	328.9	263.3	221.3	196.9	175.5
60°	292.1	330.4	377.6	391.6	342.2	309.8	276.6	222.7	189.5	168.2	154.1
62.5°	257.4	289.1	325.2	325.2	281.7	257.4	232.3	186.6	159.3	142.3	135.7
65°	223.5	246.3	272.1	269.2	232.3	210.9	191.0	154.1	133.5	121.7	115.1
67.5°	190.3	208.0	224.9	214.6	188.1	169.6	151.2	124.6	110.6	102.5	93.7
70°	160.0	174.1	182.9	173.3	146.8	131.3	118.0	100.3	89.2	78.9	73.8
72.5°	134.2	140.1	143.1	131.3	109.2	100.3	90.7	78.2	68.6	63.4	62.0
75°	104.7	109.9	107.7	98.8	80.4	73.8	66.4	57.5	55.3	52.4	50.9
77.5°	81.9	81.9	78.2	70.1	57.5	52.4	49.4	45.0	42.8	42.0	40.6
80°	58.3	57.5	55.3	46.5	39.1	36.1	36.1	33.2	32.5	31.0	31.0
82.5°	38.4	38.4	35.4	28.0	25.8	25.1	24.3	22.9	22.9	22.1	22.1
85°	22.9	21.4	17.7	15.5	14.8	14.8	14.0	13.3	14.0	13.3	13.3
87.5°	10.3	8.1	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
90°	1.0	3.9	7.8	9.8	11.8	13.2	14.7	19.6	26.5	32.3	33.3
92.5°	14.7	20.6	28.4	33.3	41.1	46.5	51.9	78.4	115.6	148.9	150.9
95°	34.3	38.2	48.0	56.8	72.5	84.2	96.0	141.1	226.3	340.0	384.0
97.5°	50.9	56.8	67.6	80.3	98.0	111.2	124.4	182.2	300.8	484.0	626.0
100°	75.4	78.4	87.2	102.9	122.5	136.2	149.9	201.8	321.3	532.9	774.0
102.5°	98.0	99.9	108.7	124.4	145.0	158.7	172.4	219.4	322.3	514.3	778.8
105°	119.5	123.4	130.3	145.0	166.5	180.2	194.0	240.0	327.2	488.9	725.9
107.5°	143.0	146.0	152.8	166.5	188.1	201.8	215.5	260.6	338.0	475.1	677.0
110°	166.5	170.5	176.3	189.1	209.7	223.9	238.1	281.2	351.7	471.2	643.7

TEST NUMBER: P1010070

CATALOG NUMBER: S122RDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	188.1	192.0	198.9	210.6	230.2	244.9	259.6	300.8	366.4	472.2	622.1
115°	210.6	215.5	221.4	233.2	252.8	266.0	279.2	321.3	381.1	476.1	607.4
117.5°	234.1	238.1	243.9	254.7	273.3	287.0	300.8	340.0	396.8	482.0	599.6
120°	255.7	259.6	265.5	274.3	293.9	307.6	321.3	359.5	412.4	487.9	592.7
122.5°	276.3	279.2	285.1	294.9	314.5	328.7	342.9	378.2	426.2	494.7	588.8
125°	293.9	296.8	302.7	314.5	334.1	347.8	361.5	396.8	440.9	501.6	583.9
127.5°	308.6	312.5	320.4	333.1	351.7	365.9	380.1	414.4	454.6	508.5	581.0
130°	321.3	325.3	335.1	348.8	368.4	382.1	395.8	430.1	467.3	516.3	579.0
132.5°	333.1	338.0	348.8	363.5	384.0	397.8	411.5	443.8	480.0	524.1	578.0
135°	344.8	348.8	360.5	375.2	397.8	411.5	425.2	456.5	490.8	530.0	577.0
137.5°	355.6	360.5	372.3	388.0	410.5	423.2	436.0	467.3	499.6	535.9	577.0
140°	368.4	372.3	384.0	399.7	421.3	434.0	446.7	476.1	506.5	539.8	576.1
142.5°	381.1	384.0	394.8	410.5	431.1	442.8	454.6	483.0	512.4	542.7	576.1
145°	393.8	397.8	407.5	422.2	441.8	452.6	463.4	489.8	517.3	544.7	574.1
147.5°	407.5	410.5	420.3	434.0	450.7	460.4	470.2	495.7	520.2	545.7	571.2
150°	421.3	424.2	432.0	444.8	459.5	468.3	477.1	499.6	522.2	544.7	568.2
152.5°	435.0	436.0	443.8	454.6	468.3	476.2	484.0	503.6	523.2	542.7	563.3
155°	447.7	448.7	454.6	465.4	476.1	483.4	490.8	507.5	524.1	540.8	557.4
157.5°	458.5	459.5	464.4	474.2	483.0	489.4	495.7	510.4	524.1	536.9	551.6
160°	469.3	470.2	474.2	482.0	489.8	495.2	500.6	512.4	524.1	533.9	545.7
162.5°	480.0	479.1	483.0	488.9	495.7	499.6	503.6	513.4	523.2	531.0	540.8
165°	487.9	486.9	488.9	494.7	499.6	502.6	505.5	514.3	521.2	527.1	533.9
167.5°	494.7	493.8	495.7	499.6	503.6	505.6	507.5	514.3	520.2	523.2	528.1
170°	501.6	499.6	500.6	503.6	505.5	507.0	508.5	513.4	518.3	520.2	523.2
172.5°	505.5	504.5	503.6	506.5	507.5	508.4	509.4	512.4	515.3	516.3	517.3
175°	508.5	507.5	506.5	508.5	508.5	509.0	509.4	511.4	513.4	512.4	513.4
177.5°	510.4	508.5	507.5	509.4	509.4	509.4	509.4	510.4	512.4	510.4	509.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P1010070

CATALOG NUMBER: S122RDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1098.9	1100.4	1102.6	1112.9	1114.4	1117.3	1115.8	1115.8	1116.6	1115.1	1115.8
5°	1146.1	1148.3	1159.4	1171.9	1174.8	1171.9	1175.6	1180.7	1180.7	1180.7	1179.3
7.5°	1190.3	1198.4	1211.0	1229.4	1233.1	1236.8	1243.4	1239.0	1240.5	1247.1	1244.9
10°	1233.1	1244.9	1258.9	1274.4	1282.5	1287.7	1290.6	1297.3	1312.8	1295.1	1301.7
12.5°	1273.7	1290.6	1305.4	1322.3	1328.2	1334.9	1337.1	1343.0	1343.0	1342.3	1347.4
15°	1300.2	1315.7	1329.0	1340.0	1341.5	1340.0	1338.6	1339.3	1341.5	1332.7	1337.8
17.5°	1306.1	1307.6	1312.0	1307.6	1308.3	1292.8	1284.0	1281.8	1261.1	1261.9	1278.8
20°	1277.4	1252.3	1245.6	1221.3	1206.6	1166.7	1165.3	1154.2	1110.7	1124.0	1121.0
22.5°	1198.4	1155.7	1098.9	1070.9	1056.8	1014.8	982.4	959.5	944.0	928.5	921.9
25°	1094.5	1025.1	944.7	889.4	881.3	842.2	782.5	754.5	721.3	711.0	728.7
27.5°	960.2	870.3	779.5	694.7	679.2	643.8	613.6	593.7	555.3	553.1	554.6
30°	778.1	687.4	611.4	556.1	517.7	501.5	481.6	466.8	451.4	457.3	458.7
32.5°	639.4	553.1	482.3	452.8	435.1	424.8	407.8	398.3	391.6	389.4	388.7
35°	508.1	450.6	418.9	390.1	379.8	372.4	359.9	355.5	349.6	350.3	350.3
37.5°	435.1	387.2	363.6	348.8	339.3	335.6	327.5	323.0	319.3	317.9	320.1
40°	375.4	342.2	327.5	314.2	306.1	304.6	300.2	295.0	290.6	291.3	293.5
42.5°	331.9	312.7	295.0	284.7	278.8	276.6	272.9	269.2	269.2	267.0	266.2
45°	297.2	281.7	267.0	257.4	253.7	250.8	246.3	245.6	242.6	243.4	244.1
47.5°	266.2	253.7	242.6	233.1	229.4	228.6	224.2	221.3	221.3	220.5	219.8
50°	238.2	225.7	216.1	210.9	205.8	204.3	203.6	202.8	201.3	201.3	202.1
52.5°	215.4	202.8	195.4	191.0	188.1	186.6	186.6	185.9	185.9	185.9	185.1
55°	190.3	180.0	174.1	172.6	171.1	170.4	169.6	168.2	167.4	168.9	167.4
57.5°	166.7	163.0	157.8	156.4	152.7	152.7	150.5	149.0	147.5	149.0	149.0
60°	148.2	143.1	140.1	135.7	132.8	129.8	126.1	125.4	123.9	123.2	122.4
62.5°	129.1	124.6	117.3	110.6	106.2	103.3	101.8	101.0	101.0	100.3	100.3
65°	107.7	97.4	93.7	91.5	90.7	90.0	88.5	87.8	88.5	87.8	88.5
67.5°	84.1	82.6	80.4	78.9	78.2	77.4	77.4	76.7	76.7	76.7	76.7
70°	73.0	69.3	68.6	67.1	67.1	66.4	66.4	66.4	66.4	65.6	67.1
72.5°	60.5	58.3	57.5	56.8	56.8	56.8	56.1	56.1	56.1	55.3	56.1
75°	49.4	48.7	47.2	47.2	46.5	47.2	46.5	46.5	45.7	46.5	46.5
77.5°	39.8	39.1	38.4	38.4	37.6	37.6	37.6	37.6	37.6	37.6	38.4
80°	30.2	29.5	28.8	29.5	28.8	29.5	28.8	28.8	29.5	28.8	28.8
82.5°	22.1	21.4	21.4	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7
85°	13.3	12.5	12.5	13.3	12.5	13.3	12.5	12.5	12.5	13.3	13.3
87.5°	5.9	6.6	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	6.6
90°	32.3	31.3	29.4	31.3	31.8	32.3	32.3	32.3	32.3	32.3	32.3
92.5°	126.4	98.9	84.3	73.5	69.6	65.6	64.7	60.7	61.7	59.8	61.7
95°	336.0	256.7	196.9	155.8	145.0	134.2	121.5	113.6	110.7	111.7	110.7
97.5°	630.9	525.1	419.3	320.4	291.0	261.6	223.4	203.8	193.0	187.1	193.0
100°	915.0	894.5	773.0	638.8	579.5	520.2	438.9	396.8	368.4	350.7	368.4
102.5°	1020.8	1136.4	1132.5	1043.4	979.7	916.0	825.9	746.5	709.3	683.8	709.3
105°	986.5	1190.3	1301.0	1313.8	1297.6	1281.4	1220.7	1159.9	1117.8	1104.1	1117.8
107.5°	914.0	1132.5	1297.1	1393.1	1412.7	1432.3	1431.3	1422.5	1409.8	1387.2	1409.8
110°	846.4	1053.2	1228.5	1353.9	1394.1	1434.3	1476.4	1495.0	1503.8	1502.8	1503.8

TEST NUMBER: P1010070

CATALOG NUMBER: S122RDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	799.4	980.7	1147.2	1283.4	1330.9	1378.4	1441.1	1475.4	1494.0	1500.9	1494.0
115°	762.2	923.8	1074.7	1203.1	1253.6	1304.0	1373.5	1418.6	1444.1	1452.9	1444.1
117.5°	736.7	876.8	1012.0	1131.5	1179.5	1227.5	1299.1	1347.1	1373.5	1380.4	1373.5
120°	717.1	843.5	965.0	1068.8	1113.4	1158.0	1226.6	1272.6	1301.0	1310.8	1301.0
122.5°	700.5	817.1	925.8	1022.8	1062.0	1101.2	1160.9	1206.0	1230.5	1238.3	1230.5
125°	684.8	791.6	892.5	978.7	1015.4	1052.2	1109.0	1146.2	1170.7	1178.6	1170.7
127.5°	670.1	766.1	859.2	941.5	975.8	1010.1	1060.0	1095.3	1116.8	1122.7	1116.8
130°	655.4	741.6	825.9	903.3	935.6	967.9	1015.9	1049.2	1068.8	1076.7	1068.8
132.5°	643.7	718.1	794.5	864.1	894.0	923.8	970.9	1004.2	1021.8	1028.7	1021.8
135°	632.9	696.6	761.2	825.9	853.3	880.7	922.9	955.2	972.8	976.7	972.8
137.5°	625.0	678.9	734.8	787.7	812.2	836.7	876.8	905.2	920.9	926.8	920.9
140°	618.2	662.3	709.3	754.4	776.0	797.5	828.8	854.3	869.0	874.9	869.0
142.5°	611.3	648.6	686.8	724.0	741.2	758.3	787.7	810.2	822.9	822.9	822.9
145°	605.4	635.8	668.1	698.5	712.7	726.9	750.4	767.1	776.9	779.8	776.9
147.5°	599.6	626.0	652.5	677.0	687.8	698.5	719.1	732.8	739.7	741.6	739.7
150°	591.7	615.2	636.8	657.4	666.2	675.0	689.7	701.5	707.3	708.3	707.3
152.5°	584.9	604.5	624.1	640.7	648.0	655.4	666.2	676.0	679.9	679.9	679.9
155°	576.1	594.7	610.3	625.0	630.4	635.8	646.6	653.4	657.4	655.4	657.4
157.5°	568.2	582.9	596.6	609.4	613.8	618.2	626.0	631.9	633.9	633.9	633.9
160°	559.4	572.1	582.9	593.7	597.1	600.5	607.4	612.3	613.3	613.3	613.3
162.5°	551.6	561.4	570.2	579.0	581.4	583.9	590.7	593.7	594.7	593.7	594.7
165°	542.7	550.6	557.4	564.3	566.2	568.2	572.1	576.1	576.1	575.1	576.1
167.5°	533.9	539.8	545.7	550.6	552.6	554.5	556.5	558.4	558.4	557.4	558.4
170°	527.1	532.0	534.9	538.8	539.8	540.8	541.8	544.7	543.7	541.8	543.7
172.5°	520.2	523.2	525.1	528.1	528.6	529.0	530.0	531.0	530.0	529.0	530.0
175°	514.3	517.3	518.3	519.2	519.7	520.2	520.2	521.2	520.2	518.3	520.2
177.5°	510.4	512.4	512.4	513.4	513.4	513.4	513.4	513.4	512.4	510.4	512.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P1010070

CATALOG NUMBER: S122RDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1118.8	1113.6	1112.2	1113.6	1112.2	1112.9	1107.7	1088.6	1093.7	1085.6	1090.0
5°	1182.2	1177.8	1168.2	1166.7	1165.3	1163.8	1156.4	1139.4	1132.8	1121.7	1121.0
7.5°	1242.7	1242.7	1235.3	1230.2	1223.5	1218.4	1208.8	1183.7	1173.4	1160.1	1152.7
10°	1302.4	1283.3	1291.4	1286.2	1270.0	1267.0	1249.3	1234.6	1214.7	1201.4	1189.6
12.5°	1345.2	1339.3	1331.9	1327.5	1323.1	1313.5	1301.7	1264.1	1253.8	1227.2	1213.9
15°	1343.7	1340.0	1342.3	1342.3	1340.8	1338.6	1329.0	1301.7	1284.0	1258.2	1235.3
17.5°	1271.5	1281.0	1290.6	1297.3	1312.0	1318.7	1327.5	1311.3	1300.2	1278.1	1253.8
20°	1145.3	1168.9	1197.0	1202.9	1216.1	1255.2	1272.9	1286.9	1291.4	1284.0	1264.1
22.5°	969.8	989.7	1057.6	1056.1	1075.3	1121.7	1173.4	1215.4	1248.6	1267.0	1259.7
25°	759.6	787.7	823.8	851.1	913.8	983.1	1047.3	1114.4	1171.9	1222.8	1235.3
27.5°	574.5	611.4	640.2	676.3	708.0	789.9	872.5	977.2	1044.3	1140.9	1191.1
30°	464.6	481.6	510.4	527.3	542.8	605.5	699.2	802.4	920.4	1031.8	1118.1
32.5°	396.8	408.6	430.0	437.3	453.6	495.6	554.6	649.0	770.7	905.7	1019.2
35°	356.2	368.8	373.2	379.8	393.1	419.6	460.2	528.8	638.7	770.7	906.4
37.5°	321.6	328.2	340.7	345.2	349.6	369.5	396.8	444.7	517.7	626.1	776.6
40°	297.2	300.9	307.5	311.2	314.2	328.2	352.5	385.0	438.8	521.4	660.1
42.5°	271.4	275.8	280.3	284.7	288.4	299.4	314.2	345.2	381.3	444.0	544.3
45°	246.3	249.3	254.4	257.4	262.6	271.4	284.7	306.1	338.5	378.3	459.5
47.5°	223.5	227.2	229.4	233.1	236.7	246.3	258.9	272.9	299.4	338.5	397.5
50°	202.8	207.2	210.2	210.9	213.9	222.7	233.1	248.5	265.5	295.7	347.4
52.5°	188.1	188.8	191.0	194.0	193.2	198.4	208.0	219.8	237.5	261.8	299.4
55°	171.1	173.3	174.8	175.5	175.5	180.0	185.1	196.2	210.2	230.1	261.8
57.5°	149.7	151.9	156.4	157.8	160.0	162.3	164.5	171.8	183.6	202.8	228.6
60°	127.6	129.1	133.5	136.4	137.9	143.8	146.8	152.7	159.3	173.3	197.7
62.5°	102.5	104.0	106.2	109.2	112.1	121.0	128.3	134.2	139.4	149.0	168.9
65°	89.2	90.0	91.5	92.2	92.9	96.6	103.3	111.4	121.0	128.3	140.1
67.5°	77.4	78.2	78.9	80.4	81.1	81.9	84.8	87.0	96.6	106.9	115.8
70°	66.4	67.9	68.6	68.6	69.3	70.8	72.3	75.2	78.2	83.3	94.4
72.5°	56.1	56.8	58.3	58.3	58.3	59.7	61.2	62.7	64.2	67.1	71.5
75°	46.5	47.9	47.9	47.9	48.7	48.7	50.2	51.6	53.1	55.3	56.8
77.5°	38.4	38.4	38.4	38.4	39.1	39.1	39.8	41.3	42.0	42.8	44.3
80°	28.8	29.5	29.5	29.5	30.2	30.2	30.2	31.7	32.5	32.5	33.9
82.5°	21.4	21.4	21.4	22.1	21.4	22.1	22.1	22.9	22.1	22.9	23.6
85°	13.3	13.3	13.3	14.0	14.0	14.0	14.0	14.0	14.0	14.0	14.8
87.5°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	7.4	6.6	6.6
90°	32.3	32.3	32.3	31.8	31.3	29.4	31.3	32.3	33.3	32.3	26.5
92.5°	60.7	64.7	65.6	69.6	73.5	84.3	98.9	126.4	150.9	148.9	115.6
95°	113.6	121.5	134.2	145.0	155.8	196.9	256.7	336.0	384.0	340.0	226.3
97.5°	203.8	223.4	261.6	291.0	320.4	419.3	525.1	630.9	626.0	484.0	300.8
100°	396.8	438.9	520.2	579.5	638.8	773.0	894.5	915.0	774.0	532.9	321.3
102.5°	746.5	825.9	916.0	979.7	1043.4	1132.5	1136.4	1020.8	778.8	514.3	322.3
105°	1159.9	1220.7	1281.4	1297.6	1313.8	1301.0	1190.3	986.5	725.9	488.9	327.2
107.5°	1422.5	1431.3	1432.3	1412.7	1393.1	1297.1	1132.5	914.0	677.0	475.1	338.0
110°	1495.0	1476.4	1434.3	1394.1	1353.9	1228.5	1053.2	846.4	643.7	471.2	351.7

TEST NUMBER: P1010070

CATALOG NUMBER: S122RDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1475.4	1441.1	1378.4	1330.9	1283.4	1147.2	980.7	799.4	622.1	472.2	366.4
115°	1418.6	1373.5	1304.0	1253.6	1203.1	1074.7	923.8	762.2	607.4	476.1	381.1
117.5°	1347.1	1299.1	1227.5	1179.5	1131.5	1012.0	876.8	736.7	599.6	482.0	396.8
120°	1272.6	1226.6	1158.0	1113.4	1068.8	965.0	843.5	717.1	592.7	487.9	412.4
122.5°	1206.0	1160.9	1101.2	1062.0	1022.8	925.8	817.1	700.5	588.8	494.7	426.2
125°	1146.2	1109.0	1052.2	1015.4	978.7	892.5	791.6	684.8	583.9	501.6	440.9
127.5°	1095.3	1060.0	1010.1	975.8	941.5	859.2	766.1	670.1	581.0	508.5	454.6
130°	1049.2	1015.9	967.9	935.6	903.3	825.9	741.6	655.4	579.0	516.3	467.3
132.5°	1004.2	970.9	923.8	894.0	864.1	794.5	718.1	643.7	578.0	524.1	480.0
135°	955.2	922.9	880.7	853.3	825.9	761.2	696.6	632.9	577.0	530.0	490.8
137.5°	905.2	876.8	836.7	812.2	787.7	734.8	678.9	625.0	577.0	535.9	499.6
140°	854.3	828.8	797.5	776.0	754.4	709.3	662.3	618.2	576.1	539.8	506.5
142.5°	810.2	787.7	758.3	741.2	724.0	686.8	648.6	611.3	576.1	542.7	512.4
145°	767.1	750.4	726.9	712.7	698.5	668.1	635.8	605.4	574.1	544.7	517.3
147.5°	732.8	719.1	698.5	687.8	677.0	652.5	626.0	599.6	571.2	545.7	520.2
150°	701.5	689.7	675.0	666.2	657.4	636.8	615.2	591.7	568.2	544.7	522.2
152.5°	676.0	666.2	655.4	648.0	640.7	624.1	604.5	584.9	563.3	542.7	523.2
155°	653.4	646.6	635.8	630.4	625.0	610.3	594.7	576.1	557.4	540.8	524.1
157.5°	631.9	626.0	618.2	613.8	609.4	596.6	582.9	568.2	551.6	536.9	524.1
160°	612.3	607.4	600.5	597.1	593.7	582.9	572.1	559.4	545.7	533.9	524.1
162.5°	593.7	590.7	583.9	581.4	579.0	570.2	561.4	551.6	540.8	531.0	523.2
165°	576.1	572.1	568.2	566.2	564.3	557.4	550.6	542.7	533.9	527.1	521.2
167.5°	558.4	556.5	554.5	552.6	550.6	545.7	539.8	533.9	528.1	523.2	520.2
170°	544.7	541.8	540.8	539.8	538.8	534.9	532.0	527.1	523.2	520.2	518.3
172.5°	531.0	530.0	529.0	528.6	528.1	525.1	523.2	520.2	517.3	516.3	515.3
175°	521.2	520.2	520.2	519.7	519.2	518.3	517.3	514.3	513.4	512.4	513.4
177.5°	513.4	513.4	513.4	513.4	513.4	512.4	512.4	510.4	509.4	510.4	512.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P1010070

CATALOG NUMBER: S122RDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1083.4	1079.7	1079.7	1077.5	1077.5	1065.7	1065.7	1069.4	1065.0	1059.8	1052.4
5°	1111.4	1103.3	1101.1	1098.1	1088.6	1073.8	1067.9	1065.7	1056.8	1045.8	1033.2
7.5°	1138.0	1124.7	1118.1	1111.4	1098.9	1078.2	1066.4	1058.3	1045.0	1028.1	1011.9
10°	1163.8	1146.8	1129.9	1121.7	1104.0	1078.2	1061.3	1048.0	1028.8	1006.0	983.1
12.5°	1187.4	1152.0	1149.0	1132.8	1107.0	1077.5	1051.7	1032.5	1008.2	981.6	955.1
15°	1208.0	1171.9	1154.2	1139.4	1105.5	1068.6	1041.4	1017.8	985.3	955.1	922.6
17.5°	1218.4	1179.3	1167.5	1143.1	1108.5	1060.5	1023.7	994.9	959.5	923.4	886.5
20°	1228.7	1183.0	1163.8	1146.8	1099.6	1045.0	1003.7	970.6	931.5	888.7	848.1
22.5°	1233.8	1183.0	1160.1	1136.5	1090.8	1028.1	979.4	940.3	894.6	851.1	802.4
25°	1225.0	1178.5	1151.2	1126.9	1075.3	1007.4	951.4	907.1	858.5	809.0	759.6
27.5°	1202.9	1168.2	1136.5	1111.4	1053.9	980.9	921.9	871.7	821.6	766.3	716.1
30°	1161.6	1146.1	1121.0	1093.0	1030.3	957.3	887.2	835.6	780.3	725.0	672.6
32.5°	1097.4	1110.7	1094.5	1070.1	1002.3	924.8	850.3	798.0	737.5	677.8	629.8
35°	1019.2	1066.4	1057.6	1040.6	972.8	890.2	815.7	752.3	691.8	631.3	583.4
37.5°	933.7	1005.2	1012.6	1002.3	938.8	854.8	772.9	711.0	649.0	587.8	539.1
40°	816.4	926.3	949.9	954.3	903.4	812.0	726.4	666.0	604.8	545.0	486.0
42.5°	708.7	847.4	876.9	895.3	858.5	770.0	683.7	616.6	556.1	502.2	443.2
45°	607.7	752.3	800.2	823.8	807.6	722.0	632.8	570.1	514.8	465.4	408.6
47.5°	503.7	649.0	716.1	753.7	753.7	673.3	584.1	522.2	469.1	427.0	376.9
50°	434.4	555.3	624.7	674.1	687.4	623.9	539.9	479.4	429.2	383.5	345.2
52.5°	370.2	478.6	536.2	587.8	626.1	570.8	490.4	435.9	386.5	343.7	313.4
55°	320.1	401.2	453.6	510.4	553.1	517.0	442.5	389.4	346.6	311.2	285.4
57.5°	272.1	342.9	385.7	435.9	481.6	454.3	394.6	348.8	311.2	280.3	257.4
60°	231.6	289.1	322.3	361.4	418.2	399.0	349.6	307.5	277.3	249.3	230.1
62.5°	196.9	242.6	270.7	298.7	350.3	341.5	303.1	270.7	244.9	221.3	205.0
65°	161.5	199.1	221.3	245.6	286.9	290.6	259.6	236.7	213.1	192.5	177.7
67.5°	130.5	160.0	180.0	200.6	233.8	244.1	222.7	203.6	183.6	166.7	153.4
70°	105.5	126.1	140.9	157.1	184.4	196.9	185.9	172.6	156.4	142.3	130.5
72.5°	83.3	96.6	105.5	118.0	140.1	152.7	151.9	140.1	128.3	118.7	109.2
75°	61.2	71.5	78.9	87.0	104.7	116.5	119.5	114.3	102.5	95.1	87.8
77.5°	46.5	52.4	56.1	62.0	74.5	84.8	89.2	87.8	79.7	73.8	68.6
80°	35.4	36.9	38.4	40.6	50.9	60.5	63.4	62.7	58.3	56.1	50.2
82.5°	25.1	25.8	26.6	27.3	31.0	39.1	42.0	43.5	39.8	37.6	32.5
85°	14.8	15.5	15.5	17.0	17.7	19.9	25.1	25.1	24.3	21.4	20.7
87.5°	7.4	7.4	6.6	6.6	7.4	8.1	9.6	11.1	9.6	8.9	8.1
90°	19.6	14.7	13.2	11.8	9.8	7.8	3.9	1.0	3.9	7.8	9.8
92.5°	78.4	51.9	46.5	41.1	33.3	28.4	20.6	14.7	20.6	28.4	33.3
95°	141.1	96.0	84.2	72.5	56.8	48.0	38.2	34.3	38.2	48.0	56.8
97.5°	182.2	124.4	111.2	98.0	80.3	67.6	56.8	50.9	56.8	67.6	80.3
100°	201.8	149.9	136.2	122.5	102.9	87.2	78.4	75.4	78.4	87.2	102.9
102.5°	219.4	172.4	158.7	145.0	124.4	108.7	99.9	98.0	99.9	108.7	124.4
105°	240.0	194.0	180.2	166.5	145.0	130.3	123.4	119.5	123.4	130.3	145.0
107.5°	260.6	215.5	201.8	188.1	166.5	152.8	146.0	143.0	146.0	152.8	166.5
110°	281.2	238.1	223.9	209.7	189.1	176.3	170.5	166.5	170.5	176.3	189.1

TEST NUMBER: P1010070

CATALOG NUMBER: S122RDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	300.8	259.6	244.9	230.2	210.6	198.9	192.0	188.1	192.0	198.9	210.6
115°	321.3	279.2	266.0	252.8	233.2	221.4	215.5	210.6	215.5	221.4	233.2
117.5°	340.0	300.8	287.0	273.3	254.7	243.9	238.1	234.1	238.1	243.9	254.7
120°	359.5	321.3	307.6	293.9	274.3	265.5	259.6	255.7	259.6	265.5	274.3
122.5°	378.2	342.9	328.7	314.5	294.9	285.1	279.2	276.3	279.2	285.1	294.9
125°	396.8	361.5	347.8	334.1	314.5	302.7	296.8	293.9	296.8	302.7	314.5
127.5°	414.4	380.1	365.9	351.7	333.1	320.4	312.5	308.6	312.5	320.4	333.1
130°	430.1	395.8	382.1	368.4	348.8	335.1	325.3	321.3	325.3	335.1	348.8
132.5°	443.8	411.5	397.8	384.0	363.5	348.8	338.0	333.1	338.0	348.8	363.5
135°	456.5	425.2	411.5	397.8	375.2	360.5	348.8	344.8	348.8	360.5	375.2
137.5°	467.3	436.0	423.2	410.5	388.0	372.3	360.5	355.6	360.5	372.3	388.0
140°	476.1	446.7	434.0	421.3	399.7	384.0	372.3	368.4	372.3	384.0	399.7
142.5°	483.0	454.6	442.8	431.1	410.5	394.8	384.0	381.1	384.0	394.8	410.5
145°	489.8	463.4	452.6	441.8	422.2	407.5	397.8	393.8	397.8	407.5	422.2
147.5°	495.7	470.2	460.4	450.7	434.0	420.3	410.5	407.5	410.5	420.3	434.0
150°	499.6	477.1	468.3	459.5	444.8	432.0	424.2	421.3	424.2	432.0	444.8
152.5°	503.6	484.0	476.2	468.3	454.6	443.8	436.0	435.0	436.0	443.8	454.6
155°	507.5	490.8	483.4	476.1	465.4	454.6	448.7	447.7	448.7	454.6	465.4
157.5°	510.4	495.7	489.4	483.0	474.2	464.4	459.5	458.5	459.5	464.4	474.2
160°	512.4	500.6	495.2	489.8	482.0	474.2	470.2	469.3	470.2	474.2	482.0
162.5°	513.4	503.6	499.6	495.7	488.9	483.0	479.1	480.0	479.1	483.0	488.9
165°	514.3	505.5	502.6	499.6	494.7	488.9	486.9	487.9	486.9	488.9	494.7
167.5°	514.3	507.5	505.6	503.6	499.6	495.7	493.8	494.7	493.8	495.7	499.6
170°	513.4	508.5	507.0	505.5	503.6	500.6	499.6	501.6	499.6	500.6	503.6
172.5°	512.4	509.4	508.4	507.5	506.5	503.6	504.5	505.5	504.5	503.6	506.5
175°	511.4	509.4	509.0	508.5	508.5	506.5	507.5	508.5	507.5	506.5	508.5
177.5°	510.4	509.4	509.4	509.4	509.4	507.5	508.5	510.4	508.5	507.5	509.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P1010070

CATALOG NUMBER: S122RDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1049.5	1050.2	1052.4	1045.8	1035.5	1031.0	1017.8	1015.5	1013.3	1013.3	1015.5
5°	1025.9	1022.9	1023.7	1011.1	996.4	987.5	969.1	972.0	962.4	956.5	958.0
7.5°	1000.1	991.9	991.2	975.0	956.5	940.3	921.1	916.7	907.9	897.5	893.1
10°	967.6	961.7	950.6	932.2	908.6	895.3	869.5	854.0	851.8	836.3	830.4
12.5°	934.4	924.1	913.0	887.2	860.7	839.3	820.1	803.1	791.3	778.1	769.2
15°	896.1	883.5	871.0	843.7	812.7	791.3	762.6	737.5	702.8	675.6	660.1
17.5°	854.0	840.0	823.1	792.8	762.6	733.1	680.0	650.5	626.1	609.9	600.3
20°	810.5	795.0	778.1	747.8	695.5	643.8	614.3	591.5	576.7	560.5	548.7
22.5°	764.8	748.6	730.1	682.9	627.6	591.5	568.6	547.2	525.8	517.0	511.1
25°	722.0	707.3	683.7	619.5	576.0	542.8	517.0	503.0	491.9	480.1	469.1
27.5°	677.8	650.5	617.3	563.5	536.2	502.2	483.8	473.5	454.3	446.2	441.0
30°	624.7	594.4	562.7	524.4	492.7	469.1	452.1	435.1	424.1	416.0	407.1
32.5°	570.8	542.1	522.2	482.3	458.7	434.4	418.2	407.8	391.6	386.5	382.8
35°	524.4	500.0	482.3	449.9	427.8	405.6	393.8	378.3	368.0	358.4	352.5
37.5°	478.6	465.4	446.9	419.6	396.0	378.3	362.1	357.0	342.9	337.8	331.9
40°	446.9	427.0	411.5	387.9	368.0	348.8	338.5	326.7	317.1	309.0	306.8
42.5°	408.6	393.8	385.0	359.2	338.5	327.5	314.9	301.6	294.3	287.6	279.5
45°	379.8	366.5	354.0	333.4	314.9	300.9	289.8	281.0	268.5	265.5	253.0
47.5°	349.6	336.3	326.7	306.1	289.1	275.8	267.7	255.9	245.6	239.0	233.1
50°	319.3	308.3	299.4	281.7	267.0	253.0	241.9	230.1	225.7	214.6	210.9
52.5°	290.6	283.2	273.6	256.7	241.9	230.1	218.3	208.7	202.1	196.2	191.8
55°	266.2	254.4	250.0	231.6	219.0	206.5	196.2	190.3	182.2	178.5	174.8
57.5°	239.0	232.3	224.9	210.9	196.9	185.1	177.7	168.9	164.5	160.0	157.1
60°	215.4	205.8	199.9	188.1	175.5	164.5	157.8	151.2	145.3	141.6	135.7
62.5°	188.1	180.7	177.0	164.5	154.1	143.8	137.9	131.3	126.9	120.2	112.8
65°	164.5	158.6	154.1	143.8	134.2	124.6	118.7	110.6	104.7	101.0	100.3
67.5°	143.8	139.4	132.8	123.2	113.6	106.2	99.6	92.9	92.2	90.7	90.7
70°	121.0	116.5	112.8	102.5	94.4	86.3	84.8	82.6	80.4	79.7	78.2
72.5°	101.0	97.4	92.9	84.1	76.0	73.8	72.3	70.8	68.6	67.9	67.1
75°	81.9	76.7	73.8	65.6	63.4	62.0	60.5	58.3	56.8	56.1	54.6
77.5°	62.7	57.5	57.5	53.1	51.6	49.4	47.9	46.5	45.7	44.3	44.3
80°	44.3	44.3	42.8	40.6	38.4	37.6	35.4	34.7	33.9	34.7	33.2
82.5°	32.5	29.5	29.5	28.0	26.6	25.8	24.3	24.3	23.6	23.6	23.6
85°	18.4	18.4	17.7	16.2	15.5	15.5	14.8	14.8	14.0	14.0	13.3
87.5°	7.4	6.6	7.4	6.6	6.6	5.9	5.9	5.9	5.2	5.9	5.2
90°	11.8	13.2	14.7	19.6	26.5	32.3	33.3	32.3	31.3	29.4	31.3
92.5°	41.1	46.5	51.9	78.4	115.6	148.9	150.9	126.4	98.9	84.3	73.5
95°	72.5	84.2	96.0	141.1	226.3	340.0	384.0	336.0	256.7	196.9	155.8
97.5°	98.0	111.2	124.4	182.2	300.8	484.0	626.0	630.9	525.1	419.3	320.4
100°	122.5	136.2	149.9	201.8	321.3	532.9	774.0	915.0	894.5	773.0	638.8
102.5°	145.0	158.7	172.4	219.4	322.3	514.3	778.8	1020.8	1136.4	1132.5	1043.4
105°	166.5	180.2	194.0	240.0	327.2	488.9	725.9	986.5	1190.3	1301.0	1313.8
107.5°	188.1	201.8	215.5	260.6	338.0	475.1	677.0	914.0	1132.5	1297.1	1393.1
110°	209.7	223.9	238.1	281.2	351.7	471.2	643.7	846.4	1053.2	1228.5	1353.9

TEST NUMBER: P1010070

CATALOG NUMBER: S122RDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	230.2	244.9	259.6	300.8	366.4	472.2	622.1	799.4	980.7	1147.2	1283.4
115°	252.8	266.0	279.2	321.3	381.1	476.1	607.4	762.2	923.8	1074.7	1203.1
117.5°	273.3	287.0	300.8	340.0	396.8	482.0	599.6	736.7	876.8	1012.0	1131.5
120°	293.9	307.6	321.3	359.5	412.4	487.9	592.7	717.1	843.5	965.0	1068.8
122.5°	314.5	328.7	342.9	378.2	426.2	494.7	588.8	700.5	817.1	925.8	1022.8
125°	334.1	347.8	361.5	396.8	440.9	501.6	583.9	684.8	791.6	892.5	978.7
127.5°	351.7	365.9	380.1	414.4	454.6	508.5	581.0	670.1	766.1	859.2	941.5
130°	368.4	382.1	395.8	430.1	467.3	516.3	579.0	655.4	741.6	825.9	903.3
132.5°	384.0	397.8	411.5	443.8	480.0	524.1	578.0	643.7	718.1	794.5	864.1
135°	397.8	411.5	425.2	456.5	490.8	530.0	577.0	632.9	696.6	761.2	825.9
137.5°	410.5	423.2	436.0	467.3	499.6	535.9	577.0	625.0	678.9	734.8	787.7
140°	421.3	434.0	446.7	476.1	506.5	539.8	576.1	618.2	662.3	709.3	754.4
142.5°	431.1	442.8	454.6	483.0	512.4	542.7	576.1	611.3	648.6	686.8	724.0
145°	441.8	452.6	463.4	489.8	517.3	544.7	574.1	605.4	635.8	668.1	698.5
147.5°	450.7	460.4	470.2	495.7	520.2	545.7	571.2	599.6	626.0	652.5	677.0
150°	459.5	468.3	477.1	499.6	522.2	544.7	568.2	591.7	615.2	636.8	657.4
152.5°	468.3	476.2	484.0	503.6	523.2	542.7	563.3	584.9	604.5	624.1	640.7
155°	476.1	483.4	490.8	507.5	524.1	540.8	557.4	576.1	594.7	610.3	625.0
157.5°	483.0	489.4	495.7	510.4	524.1	536.9	551.6	568.2	582.9	596.6	609.4
160°	489.8	495.2	500.6	512.4	524.1	533.9	545.7	559.4	572.1	582.9	593.7
162.5°	495.7	499.6	503.6	513.4	523.2	531.0	540.8	551.6	561.4	570.2	579.0
165°	499.6	502.6	505.5	514.3	521.2	527.1	533.9	542.7	550.6	557.4	564.3
167.5°	503.6	505.6	507.5	514.3	520.2	523.2	528.1	533.9	539.8	545.7	550.6
170°	505.5	507.0	508.5	513.4	518.3	520.2	523.2	527.1	532.0	534.9	538.8
172.5°	507.5	508.4	509.4	512.4	515.3	516.3	517.3	520.2	523.2	525.1	528.1
175°	508.5	509.0	509.4	511.4	513.4	512.4	513.4	514.3	517.3	518.3	519.2
177.5°	509.4	509.4	509.4	510.4	512.4	510.4	509.4	510.4	512.4	512.4	513.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P1010070

CATALOG NUMBER: S122RDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1015.5	1014.1	1009.6	1011.1	1008.9	1008.9	1007.4	1007.4	1007.4	1011.1	1008.9
5°	960.2	955.1	949.9	947.7	945.5	943.3	943.3	942.5	949.2	947.7	953.6
7.5°	891.6	890.2	879.8	879.8	876.2	874.7	878.4	879.1	879.8	881.3	885.0
10°	830.4	826.7	812.0	813.5	811.3	808.3	810.5	809.0	814.2	815.7	814.2
12.5°	758.2	751.5	735.3	727.2	718.3	711.7	719.8	713.9	734.6	740.5	756.7
15°	662.3	649.7	638.7	638.7	630.6	624.7	628.4	635.0	639.4	646.1	649.0
17.5°	598.1	593.0	584.1	578.9	576.7	574.5	574.5	577.5	587.1	586.3	592.2
20°	543.5	540.6	536.2	529.5	527.3	525.8	525.8	525.8	532.5	538.4	542.1
22.5°	505.9	503.7	500.8	491.9	487.5	486.0	489.7	491.9	497.1	501.5	505.2
25°	468.3	463.2	458.0	455.0	452.8	452.8	454.3	455.0	457.3	459.5	463.9
27.5°	437.3	433.7	426.3	418.2	418.2	416.0	417.4	418.9	424.1	431.4	435.1
30°	402.7	401.9	399.0	396.0	393.1	391.6	394.6	396.8	397.5	401.2	401.2
32.5°	377.6	372.4	367.3	364.3	362.9	362.1	362.9	365.8	365.8	370.2	375.4
35°	352.5	349.6	344.4	339.3	337.8	334.1	337.0	340.0	345.2	347.4	349.6
37.5°	325.2	321.6	319.3	317.9	314.9	315.7	313.4	317.9	322.3	321.6	323.0
40°	304.6	298.0	291.3	290.6	289.8	289.1	289.1	289.8	292.8	295.7	300.2
42.5°	278.0	275.8	269.9	264.0	262.6	261.1	259.6	262.6	268.5	273.6	275.8
45°	250.8	247.8	246.3	241.9	239.0	238.2	236.7	240.4	245.6	247.8	249.3
47.5°	225.7	224.9	220.5	221.3	219.0	219.8	219.0	221.3	221.3	223.5	224.9
50°	208.7	206.5	204.3	202.8	200.6	200.6	199.9	200.6	203.6	206.5	205.8
52.5°	191.8	188.1	187.3	186.6	185.1	186.6	184.4	185.1	188.1	189.5	188.8
55°	171.8	171.1	169.6	168.2	167.4	166.7	166.7	166.7	169.6	171.8	172.6
57.5°	156.4	152.7	149.7	149.7	146.8	146.0	147.5	148.2	150.5	151.9	153.4
60°	135.0	133.5	129.1	126.9	122.4	121.7	121.7	124.6	128.3	133.5	135.0
62.5°	112.1	109.9	109.2	109.2	109.2	109.2	109.2	109.2	109.2	109.9	109.9
65°	99.6	100.3	99.6	98.8	99.6	99.6	98.8	98.8	98.8	99.6	100.3
67.5°	89.2	88.5	89.2	88.5	87.8	87.8	87.0	87.8	88.5	89.2	89.2
70°	77.4	77.4	76.7	77.4	76.7	76.0	75.2	75.2	76.7	77.4	77.4
72.5°	66.4	66.4	65.6	65.6	64.2	64.2	64.9	64.2	64.2	66.4	66.4
75°	55.3	54.6	53.8	53.8	53.1	53.1	53.1	52.4	53.8	53.8	54.6
77.5°	43.5	43.5	43.5	42.8	42.8	42.0	42.0	42.8	42.8	42.8	43.5
80°	33.2	33.2	33.2	32.5	31.7	31.7	31.7	31.7	31.7	32.5	31.7
82.5°	22.9	22.9	22.9	22.9	22.9	22.1	22.1	22.1	22.9	22.9	22.1
85°	14.0	13.3	14.0	14.0	13.3	14.0	13.3	13.3	12.5	12.5	13.3
87.5°	5.9	5.2	4.4	4.4	5.2	4.4	4.4	4.4	5.2	4.4	4.4
90°	31.8	32.3	32.3	32.3	32.3	32.3	32.3	32.3	32.3	32.3	31.8
92.5°	69.6	65.6	64.7	60.7	61.7	59.8	61.7	60.7	64.7	65.6	69.6
95°	145.0	134.2	121.5	113.6	110.7	111.7	110.7	113.6	121.5	134.2	145.0
97.5°	291.0	261.6	223.4	203.8	193.0	187.1	193.0	203.8	223.4	261.6	291.0
100°	579.5	520.2	438.9	396.8	368.4	350.7	368.4	396.8	438.9	520.2	579.5
102.5°	979.7	916.0	825.9	746.5	709.3	683.8	709.3	746.5	825.9	916.0	979.7
105°	1297.6	1281.4	1220.7	1159.9	1117.8	1104.1	1117.8	1159.9	1220.7	1281.4	1297.6
107.5°	1412.7	1432.3	1431.3	1422.5	1409.8	1387.2	1409.8	1422.5	1431.3	1432.3	1412.7
110°	1394.1	1434.3	1476.4	1495.0	1503.8	1502.8	1503.8	1495.0	1476.4	1434.3	1394.1

TEST NUMBER: P1010070

CATALOG NUMBER: S122RDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1330.9	1378.4	1441.1	1475.4	1494.0	1500.9	1494.0	1475.4	1441.1	1378.4	1330.9
115°	1253.6	1304.0	1373.5	1418.6	1444.1	1452.9	1444.1	1418.6	1373.5	1304.0	1253.6
117.5°	1179.5	1227.5	1299.1	1347.1	1373.5	1380.4	1373.5	1347.1	1299.1	1227.5	1179.5
120°	1113.4	1158.0	1226.6	1272.6	1301.0	1310.8	1301.0	1272.6	1226.6	1158.0	1113.4
122.5°	1062.0	1101.2	1160.9	1206.0	1230.5	1238.3	1230.5	1206.0	1160.9	1101.2	1062.0
125°	1015.4	1052.2	1109.0	1146.2	1170.7	1178.6	1170.7	1146.2	1109.0	1052.2	1015.4
127.5°	975.8	1010.1	1060.0	1095.3	1116.8	1122.7	1116.8	1095.3	1060.0	1010.1	975.8
130°	935.6	967.9	1015.9	1049.2	1068.8	1076.7	1068.8	1049.2	1015.9	967.9	935.6
132.5°	894.0	923.8	970.9	1004.2	1021.8	1028.7	1021.8	1004.2	970.9	923.8	894.0
135°	853.3	880.7	922.9	955.2	972.8	976.7	972.8	955.2	922.9	880.7	853.3
137.5°	812.2	836.7	876.8	905.2	920.9	926.8	920.9	905.2	876.8	836.7	812.2
140°	776.0	797.5	828.8	854.3	869.0	874.9	869.0	854.3	828.8	797.5	776.0
142.5°	741.2	758.3	787.7	810.2	822.9	822.9	822.9	810.2	787.7	758.3	741.2
145°	712.7	726.9	750.4	767.1	776.9	779.8	776.9	767.1	750.4	726.9	712.7
147.5°	687.8	698.5	719.1	732.8	739.7	741.6	739.7	732.8	719.1	698.5	687.8
150°	666.2	675.0	689.7	701.5	707.3	708.3	707.3	701.5	689.7	675.0	666.2
152.5°	648.0	655.4	666.2	676.0	679.9	679.9	679.9	676.0	666.2	655.4	648.0
155°	630.4	635.8	646.6	653.4	657.4	655.4	657.4	653.4	646.6	635.8	630.4
157.5°	613.8	618.2	626.0	631.9	633.9	633.9	633.9	631.9	626.0	618.2	613.8
160°	597.1	600.5	607.4	612.3	613.3	613.3	613.3	612.3	607.4	600.5	597.1
162.5°	581.4	583.9	590.7	593.7	594.7	593.7	594.7	593.7	590.7	583.9	581.4
165°	566.2	568.2	572.1	576.1	576.1	575.1	576.1	576.1	572.1	568.2	566.2
167.5°	552.6	554.5	556.5	558.4	558.4	557.4	558.4	558.4	556.5	554.5	552.6
170°	539.8	540.8	541.8	544.7	543.7	541.8	543.7	544.7	541.8	540.8	539.8
172.5°	528.6	529.0	530.0	531.0	530.0	529.0	530.0	531.0	530.0	529.0	528.6
175°	519.7	520.2	520.2	521.2	520.2	518.3	520.2	521.2	520.2	520.2	519.7
177.5°	513.4	513.4	513.4	513.4	512.4	510.4	512.4	513.4	513.4	513.4	513.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P1010070

CATALOG NUMBER: S122RDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1011.1	1014.8	1013.3	1005.2	1013.3	1015.5	1020.0	1024.4	1027.3	1031.8	1035.5
5°	947.7	955.1	959.5	955.1	969.8	972.0	982.4	988.3	997.1	1004.5	1010.4
7.5°	888.0	893.9	902.7	904.2	913.0	923.4	938.1	952.9	966.9	974.2	980.9
10°	823.8	834.1	847.4	844.4	857.7	873.9	889.4	913.0	924.8	938.1	949.9
12.5°	759.6	766.3	784.0	789.9	809.0	821.6	843.0	857.7	887.2	902.7	913.0
15°	647.5	674.8	696.9	723.5	748.6	772.2	791.3	817.9	843.7	855.5	872.5
17.5°	596.6	609.2	622.5	635.7	668.2	710.2	744.1	772.9	795.0	810.5	830.4
20°	543.5	556.1	570.8	583.4	603.3	633.5	675.6	725.0	751.5	767.7	786.9
22.5°	505.9	517.7	527.3	538.4	553.9	576.0	607.7	668.9	704.3	724.2	741.2
25°	465.4	480.1	490.4	498.6	511.1	535.4	561.2	595.9	659.3	674.8	698.4
27.5°	437.3	441.8	453.6	466.1	478.6	491.9	518.5	548.0	590.7	624.7	653.4
30°	404.2	415.2	426.3	431.4	442.5	461.7	477.9	509.6	542.8	569.4	604.0
32.5°	379.1	385.7	393.1	405.6	416.0	429.2	445.5	472.0	500.0	517.0	543.5
35°	351.1	355.5	371.0	376.1	386.5	399.7	416.0	436.6	466.8	480.1	499.3
37.5°	324.5	334.8	339.3	351.1	360.6	373.9	385.7	409.3	429.2	444.7	462.4
40°	303.9	308.3	316.4	326.7	334.8	345.2	359.9	376.9	398.3	410.8	426.3
42.5°	278.8	282.5	292.8	298.7	312.0	321.6	330.4	351.1	370.2	379.8	395.3
45°	251.5	260.3	267.0	278.8	286.2	298.0	309.0	323.8	341.5	352.5	361.4
47.5°	227.9	236.7	243.4	254.4	266.2	271.4	283.2	298.7	314.9	323.8	336.3
50°	208.7	211.7	224.2	229.4	241.9	252.2	260.3	273.6	291.3	296.5	306.8
52.5°	190.3	192.5	200.6	207.2	218.3	227.2	237.5	250.0	264.8	272.9	281.0
55°	174.1	175.5	179.2	186.6	194.0	205.0	214.6	226.4	239.0	247.8	255.2
57.5°	155.6	158.6	161.5	165.9	173.3	183.6	194.0	205.0	215.4	221.3	230.8
60°	134.2	138.7	143.8	149.0	154.1	161.5	173.3	183.6	193.2	198.4	205.8
62.5°	111.4	120.2	124.6	130.5	135.0	141.6	150.5	162.3	168.9	175.5	181.4
65°	100.3	101.0	101.8	107.7	115.8	122.4	130.5	139.4	149.7	154.1	158.6
67.5°	89.2	90.0	91.5	92.2	95.1	102.5	111.4	121.0	129.1	132.0	136.4
70°	78.2	78.2	81.1	81.9	82.6	83.3	90.7	100.3	107.7	111.4	116.5
72.5°	66.4	67.1	68.6	69.3	70.8	72.3	74.5	79.7	88.5	92.2	98.1
75°	54.6	55.3	56.1	56.8	59.0	59.7	62.0	64.9	68.6	73.0	76.7
77.5°	43.5	43.5	44.3	45.7	47.2	47.9	50.2	51.6	53.1	55.3	58.3
80°	32.5	33.2	33.2	34.7	34.7	35.4	36.1	38.4	39.8	41.3	42.8
82.5°	22.1	23.6	23.6	23.6	24.3	25.1	25.8	25.8	27.3	28.0	30.2
85°	13.3	14.0	14.0	14.0	13.3	14.8	14.8	15.5	15.5	15.5	16.2
87.5°	5.2	4.4	5.2	5.2	5.2	5.9	5.2	5.2	5.9	6.6	6.6
90°	31.3	29.4	31.3	32.3	33.3	32.3	26.5	19.6	14.7	13.2	11.8
92.5°	73.5	84.3	98.9	126.4	150.9	148.9	115.6	78.4	51.9	46.5	41.1
95°	155.8	196.9	256.7	336.0	384.0	340.0	226.3	141.1	96.0	84.2	72.5
97.5°	320.4	419.3	525.1	630.9	626.0	484.0	300.8	182.2	124.4	111.2	98.0
100°	638.8	773.0	894.5	915.0	774.0	532.9	321.3	201.8	149.9	136.2	122.5
102.5°	1043.4	1132.5	1136.4	1020.8	778.8	514.3	322.3	219.4	172.4	158.7	145.0
105°	1313.8	1301.0	1190.3	986.5	725.9	488.9	327.2	240.0	194.0	180.2	166.5
107.5°	1393.1	1297.1	1132.5	914.0	677.0	475.1	338.0	260.6	215.5	201.8	188.1
110°	1353.9	1228.5	1053.2	846.4	643.7	471.2	351.7	281.2	238.1	223.9	209.7

TEST NUMBER: P1010070

CATALOG NUMBER: S122RDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1283.4	1147.2	980.7	799.4	622.1	472.2	366.4	300.8	259.6	244.9	230.2
115°	1203.1	1074.7	923.8	762.2	607.4	476.1	381.1	321.3	279.2	266.0	252.8
117.5°	1131.5	1012.0	876.8	736.7	599.6	482.0	396.8	340.0	300.8	287.0	273.3
120°	1068.8	965.0	843.5	717.1	592.7	487.9	412.4	359.5	321.3	307.6	293.9
122.5°	1022.8	925.8	817.1	700.5	588.8	494.7	426.2	378.2	342.9	328.7	314.5
125°	978.7	892.5	791.6	684.8	583.9	501.6	440.9	396.8	361.5	347.8	334.1
127.5°	941.5	859.2	766.1	670.1	581.0	508.5	454.6	414.4	380.1	365.9	351.7
130°	903.3	825.9	741.6	655.4	579.0	516.3	467.3	430.1	395.8	382.1	368.4
132.5°	864.1	794.5	718.1	643.7	578.0	524.1	480.0	443.8	411.5	397.8	384.0
135°	825.9	761.2	696.6	632.9	577.0	530.0	490.8	456.5	425.2	411.5	397.8
137.5°	787.7	734.8	678.9	625.0	577.0	535.9	499.6	467.3	436.0	423.2	410.5
140°	754.4	709.3	662.3	618.2	576.1	539.8	506.5	476.1	446.7	434.0	421.3
142.5°	724.0	686.8	648.6	611.3	576.1	542.7	512.4	483.0	454.6	442.8	431.1
145°	698.5	668.1	635.8	605.4	574.1	544.7	517.3	489.8	463.4	452.6	441.8
147.5°	677.0	652.5	626.0	599.6	571.2	545.7	520.2	495.7	470.2	460.4	450.7
150°	657.4	636.8	615.2	591.7	568.2	544.7	522.2	499.6	477.1	468.3	459.5
152.5°	640.7	624.1	604.5	584.9	563.3	542.7	523.2	503.6	484.0	476.2	468.3
155°	625.0	610.3	594.7	576.1	557.4	540.8	524.1	507.5	490.8	483.4	476.1
157.5°	609.4	596.6	582.9	568.2	551.6	536.9	524.1	510.4	495.7	489.4	483.0
160°	593.7	582.9	572.1	559.4	545.7	533.9	524.1	512.4	500.6	495.2	489.8
162.5°	579.0	570.2	561.4	551.6	540.8	531.0	523.2	513.4	503.6	499.6	495.7
165°	564.3	557.4	550.6	542.7	533.9	527.1	521.2	514.3	505.5	502.6	499.6
167.5°	550.6	545.7	539.8	533.9	528.1	523.2	520.2	514.3	507.5	505.6	503.6
170°	538.8	534.9	532.0	527.1	523.2	520.2	518.3	513.4	508.5	507.0	505.5
172.5°	528.1	525.1	523.2	520.2	517.3	516.3	515.3	512.4	509.4	508.4	507.5
175°	519.2	518.3	517.3	514.3	513.4	512.4	513.4	511.4	509.4	509.0	508.5
177.5°	513.4	512.4	512.4	510.4	509.4	510.4	512.4	510.4	509.4	509.4	509.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P1010070

CATALOG NUMBER: S122RDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1061.3	1061.3	1061.3	1061.3
2.5°	1042.1	1039.9	1053.2	1067.9
5°	1020.7	1024.4	1041.4	1062.0
7.5°	998.6	1006.7	1026.6	1053.9
10°	967.6	982.4	1012.6	1040.6
12.5°	937.4	957.3	986.0	1019.2
15°	903.4	925.6	961.0	1000.8
17.5°	865.8	890.9	932.2	975.7
20°	826.0	859.2	902.7	949.9
22.5°	781.8	821.6	866.6	918.9
25°	739.0	782.5	827.5	888.0
27.5°	696.9	739.7	789.9	851.1
30°	654.9	694.0	747.8	813.5
32.5°	609.9	650.5	707.3	774.4
35°	568.6	609.2	662.3	728.7
37.5°	524.4	567.9	618.8	687.4
40°	472.7	523.6	573.0	638.7
42.5°	430.0	483.8	531.7	593.7
45°	396.0	446.9	486.8	547.2
47.5°	364.3	405.6	446.2	502.2
50°	334.1	365.8	407.8	458.0
52.5°	303.1	330.4	366.5	413.7
55°	275.1	300.9	333.4	369.5
57.5°	249.3	267.7	300.2	332.6
60°	220.5	239.7	264.8	292.1
62.5°	196.2	210.9	234.5	257.4
65°	170.4	184.4	202.1	223.5
67.5°	146.8	159.3	173.3	190.3
70°	125.4	135.0	145.3	160.0
72.5°	102.5	112.8	122.4	134.2
75°	84.1	88.5	96.6	104.7
77.5°	64.9	70.8	75.2	81.9
80°	46.5	51.6	53.1	58.3
82.5°	31.0	33.9	36.9	38.4
85°	17.7	19.2	22.1	22.9
87.5°	6.6	7.4	8.9	10.3
90°	9.8	7.8	3.9	1.0
92.5°	33.3	28.4	20.6	14.7
95°	56.8	48.0	38.2	34.3
97.5°	80.3	67.6	56.8	50.9
100°	102.9	87.2	78.4	75.4
102.5°	124.4	108.7	99.9	98.0
105°	145.0	130.3	123.4	119.5
107.5°	166.5	152.8	146.0	143.0
110°	189.1	176.3	170.5	166.5

TEST NUMBER: P1010070

CATALOG NUMBER: S122RDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	210.6	198.9	192.0	188.1
115°	233.2	221.4	215.5	210.6
117.5°	254.7	243.9	238.1	234.1
120°	274.3	265.5	259.6	255.7
122.5°	294.9	285.1	279.2	276.3
125°	314.5	302.7	296.8	293.9
127.5°	333.1	320.4	312.5	308.6
130°	348.8	335.1	325.3	321.3
132.5°	363.5	348.8	338.0	333.1
135°	375.2	360.5	348.8	344.8
137.5°	388.0	372.3	360.5	355.6
140°	399.7	384.0	372.3	368.4
142.5°	410.5	394.8	384.0	381.1
145°	422.2	407.5	397.8	393.8
147.5°	434.0	420.3	410.5	407.5
150°	444.8	432.0	424.2	421.3
152.5°	454.6	443.8	436.0	435.0
155°	465.4	454.6	448.7	447.7
157.5°	474.2	464.4	459.5	458.5
160°	482.0	474.2	470.2	469.3
162.5°	488.9	483.0	479.1	480.0
165°	494.7	488.9	486.9	487.9
167.5°	499.6	495.7	493.8	494.7
170°	503.6	500.6	499.6	501.6
172.5°	506.5	503.6	504.5	505.5
175°	508.5	506.5	507.5	508.5
177.5°	509.4	507.5	508.5	510.4
180°	509.4	509.4	509.4	509.4

(END OF REPORT)