

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010076

Luminaire Tested: S122RDIP-B485D925UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010076
REPORT IS A COMBINATION OF REPORTS P988396 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B485D925UB30-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5431.0 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010076

CATALOG NUMBER: S122RDIP-B485D925UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1010076

CATALOG NUMBER: S122RDIP-B485D925UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42	34		
1	95	91	87	84	85	82	79	76	66	64	62	51	50	49	37	37	36	30		
2	87	80	74	69	78	72	68	64	58	55	52	46	43	41	34	32	31	26		
3	79	71	64	58	72	64	58	54	52	48	45	41	38	36	30	29	27	23		
4	73	63	55	50	66	57	51	46	47	42	38	37	34	31	28	26	24	20		
5	67	56	49	43	61	51	45	40	42	37	33	33	30	27	25	23	21	18		
6	62	51	43	38	56	46	40	35	38	33	29	30	27	24	23	21	19	16		
7	57	46	38	33	52	42	35	31	35	30	26	28	24	22	21	19	17	14		
8	53	42	34	29	48	38	32	27	32	27	23	25	22	19	20	17	16	13		
9	50	38	31	26	45	35	29	25	29	24	21	23	20	18	18	16	14	12		
10	46	35	28	24	42	32	26	22	27	22	19	22	18	16	17	15	13	11		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16945	16945	16945	16945
5°	16986	17998	17044	14379
10°	16798	19025	16917	11875
15°	16433	19030	16712	8920
20°	15995	15731	16343	7359
25°	15464	9830	15797	6261
30°	14786	6293	15187	5389
35°	13959	4837	14411	4612
40°	13038	4066	13597	4034
45°	12056	3460	12560	3387
50°	11048	2940	11565	2930
55°	9931	2556	10467	2521
60°	8940	1948	9413	1924
65°	8013	1466	8489	1663
70°	6990	1171	7540	1355
75°	5907	898	6450	1026
80°	4694	610	5046	673
85°	3263	315	3574	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 15501 cd/sqm

TEST NUMBER: P1010076

CATALOG NUMBER: S122RDIP-B485D925UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.5	1.9
10°-20°	283.4	5.2
20°-30°	364.8	6.7
30°-40°	346.1	6.4
40°-50°	296.6	5.5
50°-60°	225.9	4.2
60°-70°	142.4	2.6
70°-80°	71.1	1.3
80°-90°	21.6	0.4
90°-100°	200.3	3.7
100°-110°	705.3	13.0
110°-120°	740.7	13.6
120°-130°	609.4	11.2
130°-140°	489.5	9.0
140°-150°	369.8	6.8
150°-160°	260.0	4.8
160°-170°	153.0	2.8
170°-180°	49.8	0.9
0°-30°	749.7	13.8
0°-40°	1095.8	20.2
0°-60°	1618.2	29.8
0°-90°	1853.3	34.1
90°-120°	1646.3	30.3
90°-150°	3115.0	57.4
90°-180°	3578.0	65.9
0°-180°	5431.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1070	1070	1070	1070	1070	
5°	1071	1191	1075	952	1071	102
15°	1010	1344	1027	630	1010	284
25°	896	717	915	457	896	411
35°	735	353	759	337	735	460
45°	552	246	575	240	552	426
55°	373	170	393	168	373	336
65°	225	88	239	100	225	224
75°	106	47	115	54	106	114
85°	23	13	25	14	23	26
90°	1	33	1	33	1	4
95°	35	113	35	113	35	36
105°	120	1113	120	1113	120	128
115°	212	1465	212	1465	212	211
125°	296	1188	296	1188	296	263
135°	348	985	348	985	348	269
145°	397	786	397	786	397	249
155°	452	661	452	661	452	208
165°	492	580	492	580	492	139
175°	513	523	513	523	513	49
180°	514	514	514	514	514	

TEST NUMBER: P1010076

CATALOG NUMBER: S122RDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1077.2	1081.7	1083.9	1086.9	1093.6	1098.1	1104.7	1106.2	1105.5	1108.5	1100.3
5°	1071.3	1080.9	1089.9	1097.3	1109.2	1116.6	1124.8	1134.5	1136.7	1147.9	1141.2
7.5°	1063.1	1077.2	1089.9	1104.7	1122.6	1132.3	1144.9	1159.8	1166.5	1179.9	1183.6
10°	1049.7	1069.8	1091.4	1107.0	1131.5	1148.6	1160.5	1184.3	1200.0	1220.1	1217.1
12.5°	1028.1	1054.2	1083.2	1109.2	1141.2	1152.4	1174.7	1199.2	1219.3	1237.9	1254.3
15°	1009.5	1039.3	1071.3	1103.3	1139.7	1160.5	1182.9	1214.8	1236.4	1269.2	1283.3
17.5°	984.2	1022.2	1060.1	1095.8	1139.0	1162.8	1190.3	1221.5	1253.5	1284.8	1295.9
20°	958.2	999.1	1040.0	1088.4	1137.5	1160.5	1188.8	1227.5	1258.7	1283.3	1283.3
22.5°	926.9	976.8	1023.7	1069.8	1123.3	1156.8	1185.8	1231.2	1253.5	1258.7	1238.7
25°	895.7	945.5	996.9	1054.2	1115.2	1144.9	1177.7	1220.1	1227.5	1206.7	1154.6
27.5°	858.5	914.3	972.3	1034.1	1098.1	1135.2	1165.0	1193.3	1179.1	1123.3	1042.3
30°	820.6	880.8	946.3	1005.1	1082.4	1116.6	1141.9	1150.1	1105.5	1014.7	909.8
32.5°	781.1	839.9	909.1	979.8	1057.9	1090.6	1107.0	1085.4	1003.6	889.0	761.0
35°	735.0	801.2	873.4	947.0	1024.4	1049.0	1058.6	1005.8	900.9	752.9	625.7
37.5°	693.3	759.6	836.9	912.1	987.2	1000.6	990.9	908.3	775.2	628.6	504.4
40°	644.2	714.9	790.8	874.9	936.6	940.3	916.5	809.4	644.2	506.6	430.0
42.5°	598.9	670.3	746.2	831.7	878.6	865.9	834.0	693.3	537.9	436.7	374.9
45°	552.0	619.7	701.5	777.4	810.9	781.1	732.8	583.2	451.6	375.7	328.1
47.5°	506.6	569.9	650.9	723.9	729.8	696.3	639.0	488.8	391.3	330.3	291.6
50°	462.0	525.2	601.1	661.4	655.4	609.3	544.6	424.8	340.0	291.6	259.6
52.5°	417.3	474.6	548.3	595.9	570.6	526.0	462.0	360.1	296.8	254.4	229.9
55°	372.7	426.3	489.5	528.9	488.8	437.4	392.1	308.7	257.4	223.2	204.6
57.5°	335.5	377.9	435.9	459.8	411.4	371.2	331.8	265.6	223.2	198.6	177.1
60°	294.6	333.3	380.9	395.0	345.2	312.5	279.0	224.7	191.2	169.6	155.5
62.5°	259.6	291.6	328.1	328.1	284.2	259.6	234.3	188.2	160.7	143.6	136.9
65°	225.4	248.5	274.5	271.5	234.3	212.8	192.7	155.5	134.7	122.7	116.1
67.5°	191.9	209.8	226.9	216.5	189.7	171.1	152.5	125.7	111.6	103.4	94.5
70°	161.4	175.6	184.5	174.8	148.0	132.4	119.0	101.2	90.0	79.6	74.4
72.5°	135.4	141.3	144.3	132.4	110.1	101.2	91.5	78.9	69.2	64.0	62.5
75°	105.6	110.8	108.6	99.7	81.1	74.4	67.0	58.0	55.8	52.8	51.3
77.5°	82.6	82.6	78.9	70.7	58.0	52.8	49.8	45.4	43.1	42.4	40.9
80°	58.8	58.0	55.8	46.9	39.4	36.5	36.5	33.5	32.7	31.2	31.2
82.5°	38.7	38.7	35.7	28.3	26.0	25.3	24.5	23.1	23.1	22.3	22.3
85°	23.1	21.6	17.9	15.6	14.9	14.9	14.1	13.4	14.1	13.4	13.4
87.5°	10.4	8.2	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
90°	1.0	4.0	7.9	9.9	11.9	13.4	14.8	19.8	26.7	32.6	33.6
92.5°	14.8	20.7	28.7	33.6	41.5	47.0	52.4	79.0	116.6	150.2	152.1
95°	34.6	38.5	48.4	57.3	73.1	84.9	96.8	142.3	228.2	342.8	387.3
97.5°	51.4	57.3	68.2	81.0	98.8	112.2	125.5	183.8	303.3	488.1	631.3
100°	76.1	79.0	87.9	103.7	123.5	137.4	151.2	203.5	324.1	537.5	780.5
102.5°	98.8	100.8	109.7	125.5	146.2	160.0	173.9	221.3	325.0	518.7	785.4
105°	120.5	124.5	131.4	146.2	168.0	181.8	195.6	242.1	330.0	493.0	732.1
107.5°	144.2	147.2	154.1	168.0	189.7	203.6	217.4	262.8	340.8	479.2	682.7
110°	168.0	171.9	177.8	190.7	211.4	225.8	240.1	283.5	354.7	475.2	649.1

TEST NUMBER: P1010076

CATALOG NUMBER: S122RDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	189.7	193.6	200.6	212.4	232.2	247.0	261.8	303.3	369.5	476.2	627.4
115°	212.4	217.4	223.3	235.1	254.9	268.2	281.6	324.1	384.3	480.1	612.5
117.5°	236.1	240.1	246.0	256.9	275.6	289.5	303.3	342.8	400.1	486.1	604.6
120°	257.9	261.8	267.7	276.6	296.4	310.2	324.1	362.6	415.9	492.0	597.7
122.5°	278.6	281.6	287.5	297.4	317.1	331.5	345.8	381.4	429.8	498.9	593.8
125°	296.4	299.4	305.3	317.1	336.9	350.8	364.6	400.1	444.6	505.8	588.8
127.5°	311.2	315.2	323.1	335.9	354.7	369.0	383.3	417.9	458.4	512.8	585.9
130°	324.1	328.0	337.9	351.7	371.5	385.3	399.1	433.7	471.3	520.7	583.9
132.5°	335.9	340.8	351.7	366.5	387.3	401.1	414.9	447.5	484.1	528.6	582.9
135°	347.8	351.7	363.6	378.4	401.1	415.0	428.8	460.4	495.0	534.5	581.9
137.5°	358.6	363.6	375.4	391.2	414.0	426.8	439.6	471.3	503.9	540.4	581.9
140°	371.5	375.4	387.3	403.1	424.8	437.6	450.5	480.1	510.8	544.4	580.9
142.5°	384.3	387.3	398.1	414.0	434.7	446.6	458.4	487.1	516.7	547.3	580.9
145°	397.2	401.1	411.0	425.8	445.6	456.4	467.3	494.0	521.6	549.3	578.9
147.5°	411.0	414.0	423.8	437.7	454.5	464.4	474.2	499.9	524.6	550.3	576.0
150°	424.8	427.8	435.7	448.5	463.4	472.2	481.1	503.9	526.6	549.3	573.0
152.5°	438.7	439.6	447.5	458.4	472.2	480.2	488.1	507.8	527.6	547.3	568.1
155°	451.5	452.5	458.4	469.3	480.1	487.6	495.0	511.8	528.6	545.4	562.2
157.5°	462.4	463.4	468.3	478.2	487.1	493.5	499.9	514.7	528.6	541.4	556.2
160°	473.2	474.2	478.2	486.1	494.0	499.4	504.8	516.7	528.6	538.4	550.3
162.5°	484.1	483.1	487.1	493.0	499.9	503.8	507.8	517.7	527.6	535.5	545.4
165°	492.0	491.0	493.0	498.9	503.9	506.8	509.8	518.7	525.6	531.5	538.4
167.5°	498.9	497.9	499.9	503.9	507.8	509.8	511.8	518.7	524.6	527.6	532.5
170°	505.8	503.9	504.8	507.8	509.8	511.3	512.8	517.7	522.6	524.6	527.6
172.5°	509.8	508.8	507.8	510.8	511.8	512.8	513.7	516.7	519.7	520.7	521.6
175°	512.8	511.8	510.8	512.8	512.8	513.2	513.7	515.7	517.7	516.7	517.7
177.5°	514.7	512.8	511.8	513.7	513.7	513.7	513.7	514.7	516.7	514.7	513.7
180°	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7

TEST NUMBER: P1010076

CATALOG NUMBER: S122RDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1108.5	1110.0	1112.2	1122.6	1124.1	1127.1	1125.6	1125.6	1126.3	1124.8	1125.6
5°	1156.1	1158.3	1169.5	1182.1	1185.1	1182.1	1185.8	1191.0	1191.0	1191.0	1189.6
7.5°	1200.7	1208.9	1221.5	1240.1	1243.9	1247.6	1254.3	1249.8	1251.3	1258.0	1255.8
10°	1243.9	1255.8	1269.9	1285.5	1293.7	1298.9	1301.9	1308.6	1324.2	1306.4	1313.0
12.5°	1284.8	1301.9	1316.8	1333.9	1339.8	1346.5	1348.8	1354.7	1354.7	1354.0	1359.2
15°	1311.6	1327.2	1340.6	1351.7	1353.2	1351.7	1350.2	1351.0	1353.2	1344.3	1349.5
17.5°	1317.5	1319.0	1323.5	1319.0	1319.7	1304.1	1295.2	1293.0	1272.1	1272.9	1290.0
20°	1288.5	1263.2	1256.5	1232.0	1217.1	1176.9	1175.4	1164.3	1120.4	1133.8	1130.8
22.5°	1208.9	1165.7	1108.5	1080.2	1066.1	1023.7	990.9	967.9	952.2	936.6	929.9
25°	1104.0	1034.1	953.0	897.2	889.0	849.6	789.3	761.0	727.6	717.2	735.0
27.5°	968.6	877.8	786.3	700.8	685.2	649.5	619.0	598.9	560.2	558.0	559.4
30°	784.9	693.3	616.7	560.9	522.2	505.9	485.8	470.9	455.3	461.2	462.7
32.5°	645.0	558.0	486.5	456.8	438.9	428.5	411.4	401.7	395.0	392.8	392.1
35°	512.6	454.5	422.6	393.5	383.1	375.7	363.0	358.6	352.6	353.4	353.4
37.5°	438.9	390.6	366.8	351.9	342.2	338.5	330.3	325.8	322.1	320.6	322.9
40°	378.7	345.2	330.3	316.9	308.7	307.2	302.8	297.6	293.1	293.9	296.1
42.5°	334.8	315.4	297.6	287.2	281.2	279.0	275.3	271.5	271.5	269.3	268.6
45°	299.8	284.2	269.3	259.6	255.9	252.9	248.5	247.7	244.8	245.5	246.2
47.5°	268.6	255.9	244.8	235.1	231.4	230.6	226.2	223.2	223.2	222.4	221.7
50°	240.3	227.6	218.0	212.8	207.6	206.1	205.3	204.6	203.1	203.1	203.8
52.5°	217.2	204.6	197.1	192.7	189.7	188.2	188.2	187.5	187.5	187.5	186.7
55°	191.9	181.5	175.6	174.1	172.6	171.8	171.1	169.6	168.9	170.4	168.9
57.5°	168.1	164.4	159.2	157.7	154.0	154.0	151.8	150.3	148.8	150.3	150.3
60°	149.5	144.3	141.3	136.9	133.9	130.9	127.2	126.5	125.0	124.2	123.5
62.5°	130.2	125.7	118.3	111.6	107.1	104.2	102.7	101.9	101.9	101.2	101.2
65°	108.6	98.2	94.5	92.2	91.5	90.8	89.3	88.5	89.3	88.5	89.3
67.5°	84.8	83.3	81.1	79.6	78.9	78.1	78.1	77.4	77.4	77.4	77.4
70°	73.6	69.9	69.2	67.7	67.7	67.0	67.0	67.0	67.0	66.2	67.7
72.5°	61.0	58.8	58.0	57.3	57.3	57.3	56.5	56.5	56.5	55.8	56.5
75°	49.8	49.1	47.6	47.6	46.9	47.6	46.9	46.9	46.1	46.9	46.9
77.5°	40.2	39.4	38.7	38.7	37.9	37.9	37.9	37.9	37.9	37.9	38.7
80°	30.5	29.8	29.0	29.8	29.0	29.8	29.0	29.0	29.8	29.0	29.0
82.5°	22.3	21.6	21.6	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8
85°	13.4	12.6	12.6	13.4	12.6	13.4	12.6	12.6	12.6	13.4	13.4
87.5°	6.0	6.7	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.7
90°	32.6	31.6	29.6	31.6	32.1	32.6	32.6	32.6	32.6	32.6	32.6
92.5°	127.4	99.8	85.0	74.1	70.2	66.2	65.2	61.3	62.2	60.3	62.2
95°	338.9	258.8	198.6	157.1	146.2	135.4	122.5	114.6	111.6	112.6	111.6
97.5°	636.2	529.5	422.8	323.1	293.5	263.8	225.3	205.5	194.6	188.7	194.6
100°	922.8	902.0	779.5	644.2	584.4	524.6	442.6	400.1	371.5	353.7	371.5
102.5°	1029.5	1146.0	1142.1	1052.2	988.0	923.7	832.9	752.8	715.3	689.6	715.3
105°	994.9	1200.4	1312.0	1324.9	1308.6	1292.3	1231.0	1169.7	1127.3	1113.4	1127.3
107.5°	921.8	1142.1	1308.1	1404.9	1424.6	1444.4	1443.4	1434.5	1421.7	1399.0	1421.7
110°	853.6	1062.1	1238.9	1365.4	1405.9	1446.4	1488.9	1507.6	1516.5	1515.5	1516.5

TEST NUMBER: P1010076

CATALOG NUMBER: S122RDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	806.2	988.9	1156.9	1294.2	1342.2	1390.1	1453.3	1487.9	1506.6	1513.6	1506.6
115°	768.6	931.6	1083.8	1213.2	1264.1	1315.0	1385.1	1430.6	1456.3	1465.1	1456.3
117.5°	742.9	884.2	1020.6	1141.1	1189.5	1237.9	1310.0	1358.4	1385.1	1392.0	1385.1
120°	723.2	850.6	973.1	1077.9	1122.8	1167.8	1236.9	1283.4	1312.0	1321.9	1312.0
122.5°	706.4	824.0	933.6	1031.4	1071.0	1110.5	1170.7	1216.2	1240.9	1248.8	1240.9
125°	690.6	798.3	900.0	987.0	1024.0	1061.1	1118.4	1155.9	1180.6	1188.5	1180.6
127.5°	675.8	772.6	866.4	949.4	984.0	1018.6	1069.0	1104.5	1126.3	1132.2	1126.3
130°	660.9	747.9	832.9	910.9	943.5	976.1	1024.5	1058.1	1077.9	1085.8	1077.9
132.5°	649.1	724.2	801.2	871.4	901.5	931.6	979.1	1012.7	1030.4	1037.4	1030.4
135°	638.2	702.4	767.6	832.9	860.6	888.2	930.7	963.3	981.0	985.0	981.0
137.5°	630.3	684.7	741.0	794.3	819.0	843.7	884.2	912.9	928.7	934.6	928.7
140°	623.4	667.9	715.3	760.7	782.4	804.2	835.8	861.5	876.3	882.2	876.3
142.5°	616.5	654.0	692.6	730.1	747.4	764.7	794.3	817.0	829.9	829.9	829.9
145°	610.6	641.2	673.8	704.4	718.8	733.1	756.8	773.6	783.5	786.4	783.5
147.5°	604.6	631.3	658.0	682.7	693.6	704.4	725.2	739.0	745.9	747.9	745.9
150°	596.7	620.4	642.2	662.9	671.8	680.7	695.5	707.4	713.3	714.3	713.3
152.5°	589.8	609.6	629.3	646.1	653.5	660.9	671.8	681.7	685.6	685.6	685.6
155°	580.9	599.7	615.5	630.3	635.8	641.2	652.1	659.0	662.9	660.9	662.9
157.5°	573.0	587.8	601.7	614.5	619.0	623.4	631.3	637.2	639.2	639.2	639.2
160°	564.1	577.0	587.8	598.7	602.2	605.6	612.5	617.5	618.5	618.5	618.5
162.5°	556.2	566.1	575.0	583.9	586.3	588.8	595.7	598.7	599.7	598.7	599.7
165°	547.3	555.2	562.2	569.1	571.0	573.0	577.0	580.9	580.9	579.9	580.9
167.5°	538.4	544.4	550.3	555.2	557.2	559.2	561.2	563.1	563.1	562.2	563.1
170°	531.5	536.5	539.4	543.4	544.4	545.4	546.3	549.3	548.3	546.3	548.3
172.5°	524.6	527.6	529.5	532.5	533.0	533.5	534.5	535.5	534.5	533.5	534.5
175°	518.7	521.6	522.6	523.6	524.1	524.6	524.6	525.6	524.6	522.6	524.6
177.5°	514.7	516.7	516.7	517.7	517.7	517.7	517.7	517.7	516.7	514.7	516.7
180°	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7

TEST NUMBER: P1010076

CATALOG NUMBER: S122RDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1128.6	1123.3	1121.9	1123.3	1121.9	1122.6	1117.4	1098.1	1103.3	1095.1	1099.5
5°	1192.5	1188.1	1178.4	1176.9	1175.4	1173.9	1166.5	1149.4	1142.7	1131.5	1130.8
7.5°	1253.5	1253.5	1246.1	1240.9	1234.2	1229.0	1219.3	1194.0	1183.6	1170.2	1162.8
10°	1313.8	1294.4	1302.6	1297.4	1281.1	1278.1	1260.2	1245.4	1225.3	1211.9	1200.0
12.5°	1356.9	1351.0	1343.5	1339.1	1334.6	1325.0	1313.0	1275.1	1264.7	1237.9	1224.5
15°	1355.5	1351.7	1354.0	1354.0	1352.5	1350.2	1340.6	1313.0	1295.2	1269.2	1246.1
17.5°	1282.5	1292.2	1301.9	1308.6	1323.5	1330.2	1339.1	1322.7	1311.6	1289.2	1264.7
20°	1155.3	1179.1	1207.4	1213.4	1226.8	1266.2	1284.0	1298.2	1302.6	1295.2	1275.1
22.5°	978.3	998.4	1066.8	1065.3	1084.7	1131.5	1183.6	1226.0	1259.5	1278.1	1270.6
25°	766.3	794.5	831.0	858.5	921.7	991.7	1056.4	1124.1	1182.1	1233.4	1246.1
27.5°	579.5	616.7	645.7	682.2	714.2	796.8	880.1	985.7	1053.4	1150.9	1201.5
30°	468.7	485.8	514.8	531.9	547.5	610.8	705.3	809.4	928.4	1040.8	1127.8
32.5°	400.2	412.1	433.7	441.2	457.5	499.9	559.4	654.7	777.4	913.6	1028.1
35°	359.3	372.0	376.4	383.1	396.5	423.3	464.2	533.4	644.2	777.4	914.3
37.5°	324.4	331.1	343.7	348.2	352.6	372.7	400.2	448.6	522.2	631.6	783.4
40°	299.8	303.5	310.2	313.9	316.9	331.1	355.6	388.3	442.6	526.0	665.8
42.5°	273.8	278.2	282.7	287.2	290.9	302.0	316.9	348.2	384.6	447.8	549.0
45°	248.5	251.5	256.7	259.6	264.8	273.8	287.2	308.7	341.5	381.6	463.5
47.5°	225.4	229.1	231.4	235.1	238.8	248.5	261.1	275.3	302.0	341.5	401.0
50°	204.6	209.0	212.0	212.8	215.7	224.7	235.1	250.7	267.8	298.3	350.4
52.5°	189.7	190.4	192.7	195.7	194.9	200.1	209.8	221.7	239.5	264.1	302.0
55°	172.6	174.8	176.3	177.1	177.1	181.5	186.7	197.9	212.0	232.1	264.1
57.5°	151.0	153.3	157.7	159.2	161.4	163.7	165.9	173.3	185.2	204.6	230.6
60°	128.7	130.2	134.7	137.6	139.1	145.1	148.0	154.0	160.7	174.8	199.4
62.5°	103.4	104.9	107.1	110.1	113.1	122.0	129.4	135.4	140.6	150.3	170.4
65°	90.0	90.8	92.2	93.0	93.7	97.5	104.2	112.3	122.0	129.4	141.3
67.5°	78.1	78.9	79.6	81.1	81.8	82.6	85.6	87.8	97.5	107.9	116.8
70°	67.0	68.4	69.2	69.2	69.9	71.4	72.9	75.9	78.9	84.1	95.2
72.5°	56.5	57.3	58.8	58.8	58.8	60.3	61.7	63.2	64.7	67.7	72.2
75°	46.9	48.4	48.4	48.4	49.1	49.1	50.6	52.1	53.6	55.8	57.3
77.5°	38.7	38.7	38.7	38.7	39.4	39.4	40.2	41.7	42.4	43.1	44.6
80°	29.0	29.8	29.8	29.8	30.5	30.5	30.5	32.0	32.7	32.7	34.2
82.5°	21.6	21.6	21.6	22.3	21.6	22.3	22.3	23.1	22.3	23.1	23.8
85°	13.4	13.4	13.4	14.1	14.1	14.1	14.1	14.1	14.1	14.1	14.9
87.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	7.4	6.7	6.7
90°	32.6	32.6	32.6	32.1	31.6	29.6	31.6	32.6	33.6	32.6	26.7
92.5°	61.3	65.2	66.2	70.2	74.1	85.0	99.8	127.4	152.1	150.2	116.6
95°	114.6	122.5	135.4	146.2	157.1	198.6	258.8	338.9	387.3	342.8	228.2
97.5°	205.5	225.3	263.8	293.5	323.1	422.8	529.5	636.2	631.3	488.1	303.3
100°	400.1	442.6	524.6	584.4	644.2	779.5	902.0	922.8	780.5	537.5	324.1
102.5°	752.8	832.9	923.7	988.0	1052.2	1142.1	1146.0	1029.5	785.4	518.7	325.0
105°	1169.7	1231.0	1292.3	1308.6	1324.9	1312.0	1200.4	994.9	732.1	493.0	330.0
107.5°	1434.5	1443.4	1444.4	1424.6	1404.9	1308.1	1142.1	921.8	682.7	479.2	340.8
110°	1507.6	1488.9	1446.4	1405.9	1365.4	1238.9	1062.1	853.6	649.1	475.2	354.7

TEST NUMBER: P1010076

CATALOG NUMBER: S122RDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1487.9	1453.3	1390.1	1342.2	1294.2	1156.9	988.9	806.2	627.4	476.2	369.5
115°	1430.6	1385.1	1315.0	1264.1	1213.2	1083.8	931.6	768.6	612.5	480.1	384.3
117.5°	1358.4	1310.0	1237.9	1189.5	1141.1	1020.6	884.2	742.9	604.6	486.1	400.1
120°	1283.4	1236.9	1167.8	1122.8	1077.9	973.1	850.6	723.2	597.7	492.0	415.9
122.5°	1216.2	1170.7	1110.5	1071.0	1031.4	933.6	824.0	706.4	593.8	498.9	429.8
125°	1155.9	1118.4	1061.1	1024.0	987.0	900.0	798.3	690.6	588.8	505.8	444.6
127.5°	1104.5	1069.0	1018.6	984.0	949.4	866.4	772.6	675.8	585.9	512.8	458.4
130°	1058.1	1024.5	976.1	943.5	910.9	832.9	747.9	660.9	583.9	520.7	471.3
132.5°	1012.7	979.1	931.6	901.5	871.4	801.2	724.2	649.1	582.9	528.6	484.1
135°	963.3	930.7	888.2	860.6	832.9	767.6	702.4	638.2	581.9	534.5	495.0
137.5°	912.9	884.2	843.7	819.0	794.3	741.0	684.7	630.3	581.9	540.4	503.9
140°	861.5	835.8	804.2	782.4	760.7	715.3	667.9	623.4	580.9	544.4	510.8
142.5°	817.0	794.3	764.7	747.4	730.1	692.6	654.0	616.5	580.9	547.3	516.7
145°	773.6	756.8	733.1	718.8	704.4	673.8	641.2	610.6	578.9	549.3	521.6
147.5°	739.0	725.2	704.4	693.6	682.7	658.0	631.3	604.6	576.0	550.3	524.6
150°	707.4	695.5	680.7	671.8	662.9	642.2	620.4	596.7	573.0	549.3	526.6
152.5°	681.7	671.8	660.9	653.5	646.1	629.3	609.6	589.8	568.1	547.3	527.6
155°	659.0	652.1	641.2	635.8	630.3	615.5	599.7	580.9	562.2	545.4	528.6
157.5°	637.2	631.3	623.4	619.0	614.5	601.7	587.8	573.0	556.2	541.4	528.6
160°	617.5	612.5	605.6	602.2	598.7	587.8	577.0	564.1	550.3	538.4	528.6
162.5°	598.7	595.7	588.8	586.3	583.9	575.0	566.1	556.2	545.4	535.5	527.6
165°	580.9	577.0	573.0	571.0	569.1	562.2	555.2	547.3	538.4	531.5	525.6
167.5°	563.1	561.2	559.2	557.2	555.2	550.3	544.4	538.4	532.5	527.6	524.6
170°	549.3	546.3	545.4	544.4	543.4	539.4	536.5	531.5	527.6	524.6	522.6
172.5°	535.5	534.5	533.5	533.0	532.5	529.5	527.6	524.6	521.6	520.7	519.7
175°	525.6	524.6	524.6	524.1	523.6	522.6	521.6	518.7	517.7	516.7	517.7
177.5°	517.7	517.7	517.7	517.7	517.7	516.7	516.7	514.7	513.7	514.7	516.7
180°	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7

TEST NUMBER: P1010076

CATALOG NUMBER: S122RDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1092.8	1089.1	1089.1	1086.9	1086.9	1075.0	1075.0	1078.7	1074.2	1069.0	1061.6
5°	1121.1	1112.9	1110.7	1107.7	1098.1	1083.2	1077.2	1075.0	1066.1	1054.9	1042.3
7.5°	1147.9	1134.5	1127.8	1121.1	1108.5	1087.6	1075.7	1067.5	1054.2	1037.0	1020.7
10°	1173.9	1156.8	1139.7	1131.5	1113.7	1087.6	1070.5	1057.1	1037.8	1014.7	991.7
12.5°	1197.7	1162.0	1159.1	1142.7	1116.6	1086.9	1060.9	1041.5	1017.0	990.2	963.4
15°	1218.6	1182.1	1164.3	1149.4	1115.2	1078.0	1050.4	1026.6	993.9	963.4	930.7
17.5°	1229.0	1189.6	1177.7	1153.1	1118.1	1069.8	1032.6	1003.6	967.9	931.4	894.2
20°	1239.4	1193.3	1173.9	1156.8	1109.2	1054.2	1012.5	979.0	939.6	896.4	855.5
22.5°	1244.6	1193.3	1170.2	1146.4	1100.3	1037.0	987.9	948.5	902.4	858.5	809.4
25°	1235.7	1188.8	1161.3	1136.7	1084.7	1016.2	959.7	915.0	865.9	816.1	766.3
27.5°	1213.4	1178.4	1146.4	1121.1	1063.1	989.4	929.9	879.3	828.7	773.0	722.4
30°	1171.7	1156.1	1130.8	1102.5	1039.3	965.6	895.0	842.9	787.1	731.3	678.5
32.5°	1107.0	1120.4	1104.0	1079.5	1011.0	932.9	857.8	804.9	743.9	683.7	635.3
35°	1028.1	1075.7	1066.8	1049.7	981.3	897.9	822.8	758.8	697.8	636.8	588.5
37.5°	941.8	1014.0	1021.4	1011.0	947.0	862.2	779.6	717.2	654.7	592.9	543.8
40°	823.5	934.4	958.2	962.7	911.3	819.1	732.8	671.8	610.0	549.8	490.3
42.5°	714.9	854.8	884.5	903.1	865.9	776.7	689.6	621.9	560.9	506.6	447.1
45°	613.0	758.8	807.2	831.0	814.6	728.3	638.3	575.1	519.3	469.4	412.1
47.5°	508.1	654.7	722.4	760.3	760.3	679.2	589.2	526.7	473.1	430.7	380.2
50°	438.2	560.2	630.1	680.0	693.3	629.4	544.6	483.6	433.0	386.8	348.2
52.5°	373.5	482.8	540.8	592.9	631.6	575.8	494.7	439.7	389.8	346.7	316.2
55°	322.9	404.7	457.5	514.8	558.0	521.5	446.4	392.8	349.7	313.9	287.9
57.5°	274.5	345.9	389.1	439.7	485.8	458.3	398.0	351.9	313.9	282.7	259.6
60°	233.6	291.6	325.1	364.5	421.8	402.5	352.6	310.2	279.7	251.5	232.1
62.5°	198.6	244.8	273.0	301.3	353.4	344.4	305.8	273.0	247.0	223.2	206.8
65°	162.9	200.9	223.2	247.7	289.4	293.1	261.9	238.8	215.0	194.2	179.3
67.5°	131.7	161.4	181.5	202.4	235.8	246.2	224.7	205.3	185.2	168.1	154.7
70°	106.4	127.2	142.1	158.5	186.0	198.6	187.5	174.1	157.7	143.6	131.7
72.5°	84.1	97.5	106.4	119.0	141.3	154.0	153.3	141.3	129.4	119.8	110.1
75°	61.7	72.2	79.6	87.8	105.6	117.5	120.5	115.3	103.4	96.0	88.5
77.5°	46.9	52.8	56.5	62.5	75.1	85.6	90.0	88.5	80.3	74.4	69.2
80°	35.7	37.2	38.7	40.9	51.3	61.0	64.0	63.2	58.8	56.5	50.6
82.5°	25.3	26.0	26.8	27.5	31.2	39.4	42.4	43.9	40.2	37.9	32.7
85°	14.9	15.6	15.6	17.1	17.9	20.1	25.3	25.3	24.5	21.6	20.8
87.5°	7.4	7.4	6.7	6.7	7.4	8.2	9.7	11.2	9.7	8.9	8.2
90°	19.8	14.8	13.4	11.9	9.9	7.9	4.0	1.0	4.0	7.9	9.9
92.5°	79.0	52.4	47.0	41.5	33.6	28.7	20.7	14.8	20.7	28.7	33.6
95°	142.3	96.8	84.9	73.1	57.3	48.4	38.5	34.6	38.5	48.4	57.3
97.5°	183.8	125.5	112.2	98.8	81.0	68.2	57.3	51.4	57.3	68.2	81.0
100°	203.5	151.2	137.4	123.5	103.7	87.9	79.0	76.1	79.0	87.9	103.7
102.5°	221.3	173.9	160.0	146.2	125.5	109.7	100.8	98.8	100.8	109.7	125.5
105°	242.1	195.6	181.8	168.0	146.2	131.4	124.5	120.5	124.5	131.4	146.2
107.5°	262.8	217.4	203.6	189.7	168.0	154.1	147.2	144.2	147.2	154.1	168.0
110°	283.5	240.1	225.8	211.4	190.7	177.8	171.9	168.0	171.9	177.8	190.7

TEST NUMBER: P1010076

CATALOG NUMBER: S122RDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	303.3	261.8	247.0	232.2	212.4	200.6	193.6	189.7	193.6	200.6	212.4
115°	324.1	281.6	268.2	254.9	235.1	223.3	217.4	212.4	217.4	223.3	235.1
117.5°	342.8	303.3	289.5	275.6	256.9	246.0	240.1	236.1	240.1	246.0	256.9
120°	362.6	324.1	310.2	296.4	276.6	267.7	261.8	257.9	261.8	267.7	276.6
122.5°	381.4	345.8	331.5	317.1	297.4	287.5	281.6	278.6	281.6	287.5	297.4
125°	400.1	364.6	350.8	336.9	317.1	305.3	299.4	296.4	299.4	305.3	317.1
127.5°	417.9	383.3	369.0	354.7	335.9	323.1	315.2	311.2	315.2	323.1	335.9
130°	433.7	399.1	385.3	371.5	351.7	337.9	328.0	324.1	328.0	337.9	351.7
132.5°	447.5	414.9	401.1	387.3	366.5	351.7	340.8	335.9	340.8	351.7	366.5
135°	460.4	428.8	415.0	401.1	378.4	363.6	351.7	347.8	351.7	363.6	378.4
137.5°	471.3	439.6	426.8	414.0	391.2	375.4	363.6	358.6	363.6	375.4	391.2
140°	480.1	450.5	437.6	424.8	403.1	387.3	375.4	371.5	375.4	387.3	403.1
142.5°	487.1	458.4	446.6	434.7	414.0	398.1	387.3	384.3	387.3	398.1	414.0
145°	494.0	467.3	456.4	445.6	425.8	411.0	401.1	397.2	401.1	411.0	425.8
147.5°	499.9	474.2	464.4	454.5	437.7	423.8	414.0	411.0	414.0	423.8	437.7
150°	503.9	481.1	472.2	463.4	448.5	435.7	427.8	424.8	427.8	435.7	448.5
152.5°	507.8	488.1	480.2	472.2	458.4	447.5	439.6	438.7	439.6	447.5	458.4
155°	511.8	495.0	487.6	480.1	469.3	458.4	452.5	451.5	452.5	458.4	469.3
157.5°	514.7	499.9	493.5	487.1	478.2	468.3	463.4	462.4	463.4	468.3	478.2
160°	516.7	504.8	499.4	494.0	486.1	478.2	474.2	473.2	474.2	478.2	486.1
162.5°	517.7	507.8	503.8	499.9	493.0	487.1	483.1	484.1	483.1	487.1	493.0
165°	518.7	509.8	506.8	503.9	498.9	493.0	491.0	492.0	491.0	493.0	498.9
167.5°	518.7	511.8	509.8	507.8	503.9	499.9	497.9	498.9	497.9	499.9	503.9
170°	517.7	512.8	511.3	509.8	507.8	504.8	503.9	505.8	503.9	504.8	507.8
172.5°	516.7	513.7	512.8	511.8	510.8	507.8	508.8	509.8	508.8	507.8	510.8
175°	515.7	513.7	513.2	512.8	512.8	510.8	511.8	512.8	511.8	510.8	512.8
177.5°	514.7	513.7	513.7	513.7	513.7	511.8	512.8	514.7	512.8	511.8	513.7
180°	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7

TEST NUMBER: P1010076

CATALOG NUMBER: S122RDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1058.6	1059.4	1061.6	1054.9	1044.5	1040.0	1026.6	1024.4	1022.2	1022.2	1024.4
5°	1034.8	1031.8	1032.6	1019.9	1005.1	996.1	977.5	980.5	970.8	964.9	966.4
7.5°	1008.8	1000.6	999.9	983.5	964.9	948.5	929.2	924.7	915.8	905.4	900.9
10°	976.0	970.1	958.9	940.3	916.5	903.1	877.1	861.5	859.2	843.6	837.7
12.5°	942.6	932.2	921.0	895.0	868.2	846.6	827.3	810.1	798.2	784.9	775.9
15°	903.9	891.2	878.6	851.1	819.8	798.2	769.2	743.9	709.0	681.4	665.8
17.5°	861.5	847.3	830.2	799.7	769.2	739.5	685.9	656.2	631.6	615.2	605.6
20°	817.6	802.0	784.9	754.4	701.5	649.5	619.7	596.6	581.8	565.4	553.5
22.5°	771.5	755.1	736.5	688.9	633.1	596.6	573.6	552.0	530.4	521.5	515.5
25°	728.3	713.4	689.6	624.9	581.0	547.5	521.5	507.4	496.2	484.3	473.1
27.5°	683.7	656.2	622.7	568.4	540.8	506.6	488.0	477.6	458.3	450.1	444.9
30°	630.1	599.6	567.6	528.9	496.9	473.1	456.0	438.9	427.8	419.6	410.7
32.5°	575.8	546.8	526.7	486.5	462.7	438.2	421.8	411.4	395.0	389.8	386.1
35°	528.9	504.4	486.5	453.8	431.5	409.2	397.3	381.6	371.2	361.6	355.6
37.5°	482.8	469.4	450.8	423.3	399.5	381.6	365.3	360.1	345.9	340.7	334.8
40°	450.8	430.7	415.1	391.3	371.2	351.9	341.5	329.6	319.9	311.7	309.5
42.5°	412.1	397.3	388.3	362.3	341.5	330.3	317.7	304.3	296.8	290.1	282.0
45°	383.1	369.7	357.1	336.3	317.7	303.5	292.4	283.4	270.8	267.8	255.2
47.5°	352.6	339.2	329.6	308.7	291.6	278.2	270.0	258.1	247.7	241.0	235.1
50°	322.1	311.0	302.0	284.2	269.3	255.2	244.0	232.1	227.6	216.5	212.8
52.5°	293.1	285.7	276.0	258.9	244.0	232.1	220.2	210.5	203.8	197.9	193.4
55°	268.6	256.7	252.2	233.6	220.9	208.3	197.9	191.9	183.8	180.0	176.3
57.5°	241.0	234.3	226.9	212.8	198.6	186.7	179.3	170.4	165.9	161.4	158.5
60°	217.2	207.6	201.6	189.7	177.1	165.9	159.2	152.5	146.6	142.8	136.9
62.5°	189.7	182.3	178.5	165.9	155.5	145.1	139.1	132.4	128.0	121.3	113.8
65°	165.9	159.9	155.5	145.1	135.4	125.7	119.8	111.6	105.6	101.9	101.2
67.5°	145.1	140.6	133.9	124.2	114.6	107.1	100.4	93.7	93.0	91.5	91.5
70°	122.0	117.5	113.8	103.4	95.2	87.0	85.6	83.3	81.1	80.3	78.9
72.5°	101.9	98.2	93.7	84.8	76.6	74.4	72.9	71.4	69.2	68.4	67.7
75°	82.6	77.4	74.4	66.2	64.0	62.5	61.0	58.8	57.3	56.5	55.1
77.5°	63.2	58.0	58.0	53.6	52.1	49.8	48.4	46.9	46.1	44.6	44.6
80°	44.6	44.6	43.1	40.9	38.7	37.9	35.7	35.0	34.2	35.0	33.5
82.5°	32.7	29.8	29.8	28.3	26.8	26.0	24.5	24.5	23.8	23.8	23.8
85°	18.6	18.6	17.9	16.4	15.6	15.6	14.9	14.9	14.1	14.1	13.4
87.5°	7.4	6.7	7.4	6.7	6.7	6.0	6.0	6.0	5.2	6.0	5.2
90°	11.9	13.4	14.8	19.8	26.7	32.6	33.6	32.6	31.6	29.6	31.6
92.5°	41.5	47.0	52.4	79.0	116.6	150.2	152.1	127.4	99.8	85.0	74.1
95°	73.1	84.9	96.8	142.3	228.2	342.8	387.3	338.9	258.8	198.6	157.1
97.5°	98.8	112.2	125.5	183.8	303.3	488.1	631.3	636.2	529.5	422.8	323.1
100°	123.5	137.4	151.2	203.5	324.1	537.5	780.5	922.8	902.0	779.5	644.2
102.5°	146.2	160.0	173.9	221.3	325.0	518.7	785.4	1029.5	1146.0	1142.1	1052.2
105°	168.0	181.8	195.6	242.1	330.0	493.0	732.1	994.9	1200.4	1312.0	1324.9
107.5°	189.7	203.6	217.4	262.8	340.8	479.2	682.7	921.8	1142.1	1308.1	1404.9
110°	211.4	225.8	240.1	283.5	354.7	475.2	649.1	853.6	1062.1	1238.9	1365.4

TEST NUMBER: P1010076

CATALOG NUMBER: S122RDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	232.2	247.0	261.8	303.3	369.5	476.2	627.4	806.2	988.9	1156.9	1294.2
115°	254.9	268.2	281.6	324.1	384.3	480.1	612.5	768.6	931.6	1083.8	1213.2
117.5°	275.6	289.5	303.3	342.8	400.1	486.1	604.6	742.9	884.2	1020.6	1141.1
120°	296.4	310.2	324.1	362.6	415.9	492.0	597.7	723.2	850.6	973.1	1077.9
122.5°	317.1	331.5	345.8	381.4	429.8	498.9	593.8	706.4	824.0	933.6	1031.4
125°	336.9	350.8	364.6	400.1	444.6	505.8	588.8	690.6	798.3	900.0	987.0
127.5°	354.7	369.0	383.3	417.9	458.4	512.8	585.9	675.8	772.6	866.4	949.4
130°	371.5	385.3	399.1	433.7	471.3	520.7	583.9	660.9	747.9	832.9	910.9
132.5°	387.3	401.1	414.9	447.5	484.1	528.6	582.9	649.1	724.2	801.2	871.4
135°	401.1	415.0	428.8	460.4	495.0	534.5	581.9	638.2	702.4	767.6	832.9
137.5°	414.0	426.8	439.6	471.3	503.9	540.4	581.9	630.3	684.7	741.0	794.3
140°	424.8	437.6	450.5	480.1	510.8	544.4	580.9	623.4	667.9	715.3	760.7
142.5°	434.7	446.6	458.4	487.1	516.7	547.3	580.9	616.5	654.0	692.6	730.1
145°	445.6	456.4	467.3	494.0	521.6	549.3	578.9	610.6	641.2	673.8	704.4
147.5°	454.5	464.4	474.2	499.9	524.6	550.3	576.0	604.6	631.3	658.0	682.7
150°	463.4	472.2	481.1	503.9	526.6	549.3	573.0	596.7	620.4	642.2	662.9
152.5°	472.2	480.2	488.1	507.8	527.6	547.3	568.1	589.8	609.6	629.3	646.1
155°	480.1	487.6	495.0	511.8	528.6	545.4	562.2	580.9	599.7	615.5	630.3
157.5°	487.1	493.5	499.9	514.7	528.6	541.4	556.2	573.0	587.8	601.7	614.5
160°	494.0	499.4	504.8	516.7	528.6	538.4	550.3	564.1	577.0	587.8	598.7
162.5°	499.9	503.8	507.8	517.7	527.6	535.5	545.4	556.2	566.1	575.0	583.9
165°	503.9	506.8	509.8	518.7	525.6	531.5	538.4	547.3	555.2	562.2	569.1
167.5°	507.8	509.8	511.8	518.7	524.6	527.6	532.5	538.4	544.4	550.3	555.2
170°	509.8	511.3	512.8	517.7	522.6	524.6	527.6	531.5	536.5	539.4	543.4
172.5°	511.8	512.8	513.7	516.7	519.7	520.7	521.6	524.6	527.6	529.5	532.5
175°	512.8	513.2	513.7	515.7	517.7	516.7	517.7	518.7	521.6	522.6	523.6
177.5°	513.7	513.7	513.7	514.7	516.7	514.7	513.7	514.7	516.7	516.7	517.7
180°	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7

TEST NUMBER: P1010076

CATALOG NUMBER: S122RDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1024.4	1022.9	1018.4	1019.9	1017.7	1017.7	1016.2	1016.2	1016.2	1019.9	1017.7
5°	968.6	963.4	958.2	956.0	953.7	951.5	951.5	950.8	957.4	956.0	961.9
7.5°	899.4	897.9	887.5	887.5	883.8	882.3	886.0	886.8	887.5	889.0	892.7
10°	837.7	834.0	819.1	820.6	818.3	815.4	817.6	816.1	821.3	822.8	821.3
12.5°	764.8	758.1	741.7	733.5	724.6	717.9	726.1	720.1	741.0	746.9	763.3
15°	668.1	655.4	644.2	644.2	636.1	630.1	633.8	640.5	645.0	651.7	654.7
17.5°	603.3	598.1	589.2	584.0	581.8	579.5	579.5	582.5	592.2	591.4	597.4
20°	548.3	545.3	540.8	534.1	531.9	530.4	530.4	530.4	537.1	543.1	546.8
22.5°	510.3	508.1	505.1	496.2	491.7	490.3	494.0	496.2	501.4	505.9	509.6
25°	472.4	467.2	462.0	459.0	456.8	456.8	458.3	459.0	461.2	463.5	467.9
27.5°	441.2	437.4	430.0	421.8	421.8	419.6	421.1	422.6	427.8	435.2	438.9
30°	406.2	405.4	402.5	399.5	396.5	395.0	398.0	400.2	401.0	404.7	404.7
32.5°	380.9	375.7	370.5	367.5	366.0	365.3	366.0	369.0	369.0	373.5	378.7
35°	355.6	352.6	347.4	342.2	340.7	337.0	340.0	343.0	348.2	350.4	352.6
37.5°	328.1	324.4	322.1	320.6	317.7	318.4	316.2	320.6	325.1	324.4	325.8
40°	307.2	300.6	293.9	293.1	292.4	291.6	291.6	292.4	295.3	298.3	302.8
42.5°	280.5	278.2	272.3	266.3	264.8	263.4	261.9	264.8	270.8	276.0	278.2
45°	252.9	250.0	248.5	244.0	241.0	240.3	238.8	242.5	247.7	250.0	251.5
47.5°	227.6	226.9	222.4	223.2	220.9	221.7	220.9	223.2	223.2	225.4	226.9
50°	210.5	208.3	206.1	204.6	202.4	202.4	201.6	202.4	205.3	208.3	207.6
52.5°	193.4	189.7	189.0	188.2	186.7	188.2	186.0	186.7	189.7	191.2	190.4
55°	173.3	172.6	171.1	169.6	168.9	168.1	168.1	168.1	171.1	173.3	174.1
57.5°	157.7	154.0	151.0	151.0	148.0	147.3	148.8	149.5	151.8	153.3	154.7
60°	136.1	134.7	130.2	128.0	123.5	122.7	122.7	125.7	129.4	134.7	136.1
62.5°	113.1	110.8	110.1	110.1	110.1	110.1	110.1	110.1	110.1	110.8	110.8
65°	100.4	101.2	100.4	99.7	100.4	100.4	99.7	99.7	99.7	100.4	101.2
67.5°	90.0	89.3	90.0	89.3	88.5	88.5	87.8	88.5	89.3	90.0	90.0
70°	78.1	78.1	77.4	78.1	77.4	76.6	75.9	75.9	77.4	78.1	78.1
72.5°	67.0	67.0	66.2	66.2	64.7	64.7	65.5	64.7	64.7	67.0	67.0
75°	55.8	55.1	54.3	54.3	53.6	53.6	53.6	52.8	54.3	54.3	55.1
77.5°	43.9	43.9	43.9	43.1	43.1	42.4	42.4	43.1	43.1	43.1	43.9
80°	33.5	33.5	33.5	32.7	32.0	32.0	32.0	32.0	32.0	32.7	32.0
82.5°	23.1	23.1	23.1	23.1	23.1	22.3	22.3	22.3	23.1	23.1	22.3
85°	14.1	13.4	14.1	14.1	13.4	14.1	13.4	13.4	12.6	12.6	13.4
87.5°	6.0	5.2	4.5	4.5	5.2	4.5	4.5	4.5	5.2	4.5	4.5
90°	32.1	32.6	32.6	32.6	32.6	32.6	32.6	32.6	32.6	32.6	32.1
92.5°	70.2	66.2	65.2	61.3	62.2	60.3	62.2	61.3	65.2	66.2	70.2
95°	146.2	135.4	122.5	114.6	111.6	112.6	111.6	114.6	122.5	135.4	146.2
97.5°	293.5	263.8	225.3	205.5	194.6	188.7	194.6	205.5	225.3	263.8	293.5
100°	584.4	524.6	442.6	400.1	371.5	353.7	371.5	400.1	442.6	524.6	584.4
102.5°	988.0	923.7	832.9	752.8	715.3	689.6	715.3	752.8	832.9	923.7	988.0
105°	1308.6	1292.3	1231.0	1169.7	1127.3	1113.4	1127.3	1169.7	1231.0	1292.3	1308.6
107.5°	1424.6	1444.4	1443.4	1434.5	1421.7	1399.0	1421.7	1434.5	1443.4	1444.4	1424.6
110°	1405.9	1446.4	1488.9	1507.6	1516.5	1515.5	1516.5	1507.6	1488.9	1446.4	1405.9

TEST NUMBER: P1010076

CATALOG NUMBER: S122RDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1342.2	1390.1	1453.3	1487.9	1506.6	1513.6	1506.6	1487.9	1453.3	1390.1	1342.2
115°	1264.1	1315.0	1385.1	1430.6	1456.3	1465.1	1456.3	1430.6	1385.1	1315.0	1264.1
117.5°	1189.5	1237.9	1310.0	1358.4	1385.1	1392.0	1385.1	1358.4	1310.0	1237.9	1189.5
120°	1122.8	1167.8	1236.9	1283.4	1312.0	1321.9	1312.0	1283.4	1236.9	1167.8	1122.8
122.5°	1071.0	1110.5	1170.7	1216.2	1240.9	1248.8	1240.9	1216.2	1170.7	1110.5	1071.0
125°	1024.0	1061.1	1118.4	1155.9	1180.6	1188.5	1180.6	1155.9	1118.4	1061.1	1024.0
127.5°	984.0	1018.6	1069.0	1104.5	1126.3	1132.2	1126.3	1104.5	1069.0	1018.6	984.0
130°	943.5	976.1	1024.5	1058.1	1077.9	1085.8	1077.9	1058.1	1024.5	976.1	943.5
132.5°	901.5	931.6	979.1	1012.7	1030.4	1037.4	1030.4	1012.7	979.1	931.6	901.5
135°	860.6	888.2	930.7	963.3	981.0	985.0	981.0	963.3	930.7	888.2	860.6
137.5°	819.0	843.7	884.2	912.9	928.7	934.6	928.7	912.9	884.2	843.7	819.0
140°	782.4	804.2	835.8	861.5	876.3	882.2	876.3	861.5	835.8	804.2	782.4
142.5°	747.4	764.7	794.3	817.0	829.9	829.9	829.9	817.0	794.3	764.7	747.4
145°	718.8	733.1	756.8	773.6	783.5	786.4	783.5	773.6	756.8	733.1	718.8
147.5°	693.6	704.4	725.2	739.0	745.9	747.9	745.9	739.0	725.2	704.4	693.6
150°	671.8	680.7	695.5	707.4	713.3	714.3	713.3	707.4	695.5	680.7	671.8
152.5°	653.5	660.9	671.8	681.7	685.6	685.6	685.6	681.7	671.8	660.9	653.5
155°	635.8	641.2	652.1	659.0	662.9	660.9	662.9	659.0	652.1	641.2	635.8
157.5°	619.0	623.4	631.3	637.2	639.2	639.2	639.2	637.2	631.3	623.4	619.0
160°	602.2	605.6	612.5	617.5	618.5	618.5	618.5	617.5	612.5	605.6	602.2
162.5°	586.3	588.8	595.7	598.7	599.7	598.7	599.7	598.7	595.7	588.8	586.3
165°	571.0	573.0	577.0	580.9	580.9	579.9	580.9	580.9	577.0	573.0	571.0
167.5°	557.2	559.2	561.2	563.1	563.1	562.2	563.1	563.1	561.2	559.2	557.2
170°	544.4	545.4	546.3	549.3	548.3	546.3	548.3	549.3	546.3	545.4	544.4
172.5°	533.0	533.5	534.5	535.5	534.5	533.5	534.5	535.5	534.5	533.5	533.0
175°	524.1	524.6	524.6	525.6	524.6	522.6	524.6	525.6	524.6	524.6	524.1
177.5°	517.7	517.7	517.7	517.7	516.7	514.7	516.7	517.7	517.7	517.7	517.7
180°	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7

TEST NUMBER: P1010076

CATALOG NUMBER: S122RDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5	1070.5
2.5°	1019.9	1023.7	1022.2	1014.0	1022.2	1024.4	1028.9	1033.3	1036.3	1040.8	1044.5
5°	956.0	963.4	967.9	963.4	978.3	980.5	990.9	996.9	1005.8	1013.2	1019.2
7.5°	895.7	901.7	910.6	912.1	921.0	931.4	946.3	961.2	975.3	982.7	989.4
10°	831.0	841.4	854.8	851.8	865.2	881.6	897.2	921.0	932.9	946.3	958.2
12.5°	766.3	773.0	790.8	796.8	816.1	828.7	850.3	865.2	895.0	910.6	921.0
15°	653.2	680.7	703.0	729.8	755.1	778.9	798.2	825.0	851.1	863.0	880.1
17.5°	601.8	614.5	627.9	641.3	674.0	716.4	750.6	779.6	802.0	817.6	837.7
20°	548.3	560.9	575.8	588.5	608.5	639.0	681.4	731.3	758.1	774.4	793.8
22.5°	510.3	522.2	531.9	543.1	558.7	581.0	613.0	674.8	710.5	730.5	747.7
25°	469.4	484.3	494.7	502.9	515.5	540.1	566.1	601.1	665.1	680.7	704.5
27.5°	441.2	445.6	457.5	470.2	482.8	496.2	523.0	552.7	595.9	630.1	659.1
30°	407.7	418.8	430.0	435.2	446.4	465.7	482.1	514.1	547.5	574.3	609.3
32.5°	382.4	389.1	396.5	409.2	419.6	433.0	449.3	476.1	504.4	521.5	548.3
35°	354.1	358.6	374.2	379.4	389.8	403.2	419.6	440.4	470.9	484.3	503.6
37.5°	327.3	337.7	342.2	354.1	363.8	377.2	389.1	412.9	433.0	448.6	466.4
40°	306.5	311.0	319.1	329.6	337.7	348.2	363.0	380.2	401.7	414.4	430.0
42.5°	281.2	284.9	295.3	301.3	314.7	324.4	333.3	354.1	373.5	383.1	398.8
45°	253.7	262.6	269.3	281.2	288.6	300.6	311.7	326.6	344.4	355.6	364.5
47.5°	229.9	238.8	245.5	256.7	268.6	273.8	285.7	301.3	317.7	326.6	339.2
50°	210.5	213.5	226.2	231.4	244.0	254.4	262.6	276.0	293.9	299.1	309.5
52.5°	191.9	194.2	202.4	209.0	220.2	229.1	239.5	252.2	267.1	275.3	283.4
55°	175.6	177.1	180.8	188.2	195.7	206.8	216.5	228.4	241.0	250.0	257.4
57.5°	157.0	159.9	162.9	167.4	174.8	185.2	195.7	206.8	217.2	223.2	232.9
60°	135.4	139.9	145.1	150.3	155.5	162.9	174.8	185.2	194.9	200.1	207.6
62.5°	112.3	121.3	125.7	131.7	136.1	142.8	151.8	163.7	170.4	177.1	183.0
65°	101.2	101.9	102.7	108.6	116.8	123.5	131.7	140.6	151.0	155.5	159.9
67.5°	90.0	90.8	92.2	93.0	96.0	103.4	112.3	122.0	130.2	133.2	137.6
70°	78.9	78.9	81.8	82.6	83.3	84.1	91.5	101.2	108.6	112.3	117.5
72.5°	67.0	67.7	69.2	69.9	71.4	72.9	75.1	80.3	89.3	93.0	98.9
75°	55.1	55.8	56.5	57.3	59.5	60.3	62.5	65.5	69.2	73.6	77.4
77.5°	43.9	43.9	44.6	46.1	47.6	48.4	50.6	52.1	53.6	55.8	58.8
80°	32.7	33.5	33.5	35.0	35.0	35.7	36.5	38.7	40.2	41.7	43.1
82.5°	22.3	23.8	23.8	23.8	24.5	25.3	26.0	26.0	27.5	28.3	30.5
85°	13.4	14.1	14.1	14.1	13.4	14.9	14.9	15.6	15.6	15.6	16.4
87.5°	5.2	4.5	5.2	5.2	5.2	6.0	5.2	5.2	6.0	6.7	6.7
90°	31.6	29.6	31.6	32.6	33.6	32.6	26.7	19.8	14.8	13.4	11.9
92.5°	74.1	85.0	99.8	127.4	152.1	150.2	116.6	79.0	52.4	47.0	41.5
95°	157.1	198.6	258.8	338.9	387.3	342.8	228.2	142.3	96.8	84.9	73.1
97.5°	323.1	422.8	529.5	636.2	631.3	488.1	303.3	183.8	125.5	112.2	98.8
100°	644.2	779.5	902.0	922.8	780.5	537.5	324.1	203.5	151.2	137.4	123.5
102.5°	1052.2	1142.1	1146.0	1029.5	785.4	518.7	325.0	221.3	173.9	160.0	146.2
105°	1324.9	1312.0	1200.4	994.9	732.1	493.0	330.0	242.1	195.6	181.8	168.0
107.5°	1404.9	1308.1	1142.1	921.8	682.7	479.2	340.8	262.8	217.4	203.6	189.7
110°	1365.4	1238.9	1062.1	853.6	649.1	475.2	354.7	283.5	240.1	225.8	211.4

TEST NUMBER: P1010076

CATALOG NUMBER: S122RDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1294.2	1156.9	988.9	806.2	627.4	476.2	369.5	303.3	261.8	247.0	232.2
115°	1213.2	1083.8	931.6	768.6	612.5	480.1	384.3	324.1	281.6	268.2	254.9
117.5°	1141.1	1020.6	884.2	742.9	604.6	486.1	400.1	342.8	303.3	289.5	275.6
120°	1077.9	973.1	850.6	723.2	597.7	492.0	415.9	362.6	324.1	310.2	296.4
122.5°	1031.4	933.6	824.0	706.4	593.8	498.9	429.8	381.4	345.8	331.5	317.1
125°	987.0	900.0	798.3	690.6	588.8	505.8	444.6	400.1	364.6	350.8	336.9
127.5°	949.4	866.4	772.6	675.8	585.9	512.8	458.4	417.9	383.3	369.0	354.7
130°	910.9	832.9	747.9	660.9	583.9	520.7	471.3	433.7	399.1	385.3	371.5
132.5°	871.4	801.2	724.2	649.1	582.9	528.6	484.1	447.5	414.9	401.1	387.3
135°	832.9	767.6	702.4	638.2	581.9	534.5	495.0	460.4	428.8	415.0	401.1
137.5°	794.3	741.0	684.7	630.3	581.9	540.4	503.9	471.3	439.6	426.8	414.0
140°	760.7	715.3	667.9	623.4	580.9	544.4	510.8	480.1	450.5	437.6	424.8
142.5°	730.1	692.6	654.0	616.5	580.9	547.3	516.7	487.1	458.4	446.6	434.7
145°	704.4	673.8	641.2	610.6	578.9	549.3	521.6	494.0	467.3	456.4	445.6
147.5°	682.7	658.0	631.3	604.6	576.0	550.3	524.6	499.9	474.2	464.4	454.5
150°	662.9	642.2	620.4	596.7	573.0	549.3	526.6	503.9	481.1	472.2	463.4
152.5°	646.1	629.3	609.6	589.8	568.1	547.3	527.6	507.8	488.1	480.2	472.2
155°	630.3	615.5	599.7	580.9	562.2	545.4	528.6	511.8	495.0	487.6	480.1
157.5°	614.5	601.7	587.8	573.0	556.2	541.4	528.6	514.7	499.9	493.5	487.1
160°	598.7	587.8	577.0	564.1	550.3	538.4	528.6	516.7	504.8	499.4	494.0
162.5°	583.9	575.0	566.1	556.2	545.4	535.5	527.6	517.7	507.8	503.8	499.9
165°	569.1	562.2	555.2	547.3	538.4	531.5	525.6	518.7	509.8	506.8	503.9
167.5°	555.2	550.3	544.4	538.4	532.5	527.6	524.6	518.7	511.8	509.8	507.8
170°	543.4	539.4	536.5	531.5	527.6	524.6	522.6	517.7	512.8	511.3	509.8
172.5°	532.5	529.5	527.6	524.6	521.6	520.7	519.7	516.7	513.7	512.8	511.8
175°	523.6	522.6	521.6	518.7	517.7	516.7	517.7	515.7	513.7	513.2	512.8
177.5°	517.7	516.7	516.7	514.7	513.7	514.7	516.7	514.7	513.7	513.7	513.7
180°	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7	513.7

TEST NUMBER: P1010076

CATALOG NUMBER: S122RDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1070.5	1070.5	1070.5	1070.5
2.5°	1051.2	1049.0	1062.3	1077.2
5°	1029.6	1033.3	1050.4	1071.3
7.5°	1007.3	1015.5	1035.6	1063.1
10°	976.0	990.9	1021.4	1049.7
12.5°	945.5	965.6	994.6	1028.1
15°	911.3	933.6	969.3	1009.5
17.5°	873.4	898.7	940.3	984.2
20°	833.2	866.7	910.6	958.2
22.5°	788.6	828.7	874.1	926.9
25°	745.4	789.3	834.7	895.7
27.5°	703.0	746.2	796.8	858.5
30°	660.6	700.0	754.4	820.6
32.5°	615.2	656.2	713.4	781.1
35°	573.6	614.5	668.1	735.0
37.5°	528.9	572.8	624.2	693.3
40°	476.9	528.2	578.0	644.2
42.5°	433.7	488.0	536.4	598.9
45°	399.5	450.8	491.0	552.0
47.5°	367.5	409.2	450.1	506.6
50°	337.0	369.0	411.4	462.0
52.5°	305.8	333.3	369.7	417.3
55°	277.5	303.5	336.3	372.7
57.5°	251.5	270.0	302.8	335.5
60°	222.4	241.8	267.1	294.6
62.5°	197.9	212.8	236.6	259.6
65°	171.8	186.0	203.8	225.4
67.5°	148.0	160.7	174.8	191.9
70°	126.5	136.1	146.6	161.4
72.5°	103.4	113.8	123.5	135.4
75°	84.8	89.3	97.5	105.6
77.5°	65.5	71.4	75.9	82.6
80°	46.9	52.1	53.6	58.8
82.5°	31.2	34.2	37.2	38.7
85°	17.9	19.3	22.3	23.1
87.5°	6.7	7.4	8.9	10.4
90°	9.9	7.9	4.0	1.0
92.5°	33.6	28.7	20.7	14.8
95°	57.3	48.4	38.5	34.6
97.5°	81.0	68.2	57.3	51.4
100°	103.7	87.9	79.0	76.1
102.5°	125.5	109.7	100.8	98.8
105°	146.2	131.4	124.5	120.5
107.5°	168.0	154.1	147.2	144.2
110°	190.7	177.8	171.9	168.0

TEST NUMBER: P1010076

CATALOG NUMBER: S122RDIP-B485D925UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	212.4	200.6	193.6	189.7
115°	235.1	223.3	217.4	212.4
117.5°	256.9	246.0	240.1	236.1
120°	276.6	267.7	261.8	257.9
122.5°	297.4	287.5	281.6	278.6
125°	317.1	305.3	299.4	296.4
127.5°	335.9	323.1	315.2	311.2
130°	351.7	337.9	328.0	324.1
132.5°	366.5	351.7	340.8	335.9
135°	378.4	363.6	351.7	347.8
137.5°	391.2	375.4	363.6	358.6
140°	403.1	387.3	375.4	371.5
142.5°	414.0	398.1	387.3	384.3
145°	425.8	411.0	401.1	397.2
147.5°	437.7	423.8	414.0	411.0
150°	448.5	435.7	427.8	424.8
152.5°	458.4	447.5	439.6	438.7
155°	469.3	458.4	452.5	451.5
157.5°	478.2	468.3	463.4	462.4
160°	486.1	478.2	474.2	473.2
162.5°	493.0	487.1	483.1	484.1
165°	498.9	493.0	491.0	492.0
167.5°	503.9	499.9	497.9	498.9
170°	507.8	504.8	503.9	505.8
172.5°	510.8	507.8	508.8	509.8
175°	512.8	510.8	511.8	512.8
177.5°	513.7	511.8	512.8	514.7
180°	513.7	513.7	513.7	513.7

(END OF REPORT)