

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010099

Luminaire Tested: S122RDIP-B675D1080UB27-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010099
REPORT IS A COMBINATION OF REPORTS P988419 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B675D1080UB27-4F0-XX-W2A-A1
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6347.0 lumens
Efficiency: N/A
Efficacy: 89.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010099

CATALOG NUMBER: S122RDIP-B675D1080UB27-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1010099

CATALOG NUMBER: S122RDIP-B675D1080UB27-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	41	41	41	35
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	37	35	35	35	30
3	81	72	65	60	73	66	60	55	55	50	47	44	41	39	34	32	31	31	31	26
4	74	64	57	51	67	59	52	47	49	44	41	40	36	34	31	29	27	27	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	24	24	21
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	24	22	22	22	19
7	59	47	39	34	53	43	37	32	36	31	28	30	26	24	24	22	20	20	20	17
8	54	43	35	30	50	40	33	29	33	28	25	28	24	21	22	20	18	18	18	15
9	51	39	32	27	46	36	30	26	31	26	22	26	22	19	21	18	16	16	16	14
10	48	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	15	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23174	23174	23174	23174
5°	23228	24614	23309	19664
10°	22972	26017	23135	16239
15°	22474	26025	22855	12199
20°	21875	21513	22351	10065
25°	21147	13443	21605	8562
30°	20220	8607	20769	7371
35°	19090	6615	19708	6308
40°	17833	5560	18594	5517
45°	16487	4732	17175	4632
50°	15109	4020	15814	4006
55°	13582	3495	14314	3448
60°	12226	2664	12872	2633
65°	10960	2006	11610	2274
70°	9562	1601	10311	1854
75°	8083	1227	8822	1403
80°	6419	835	6906	919
85°	4450	430	4887	454

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 21199 cd/sqm

TEST NUMBER: P1010099

CATALOG NUMBER: S122RDIP-B675D1080UB27-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.9	2.2
10°-20°	387.6	6.1
20°-30°	498.8	7.9
30°-40°	473.3	7.5
40°-50°	405.6	6.4
50°-60°	308.9	4.9
60°-70°	194.8	3.1
70°-80°	97.2	1.5
80°-90°	28.9	0.5
90°-100°	84.4	1.3
100°-110°	268.2	4.2
110°-120°	458.9	7.2
120°-130°	603.6	9.5
130°-140°	677.5	10.7
140°-150°	664.4	10.5
150°-160°	557.3	8.8
160°-170°	369.6	5.8
170°-180°	129.2	2.0
0°-30°	1025.3	16.2
0°-40°	1498.6	23.6
0°-60°	2213.0	34.9
0°-90°	2533.9	39.9
90°-120°	811.5	12.8
90°-150°	2757.0	43.4
90°-180°	3813.0	60.1
0°-180°	6347.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1464	1464	1464	1464	1464	
5°	1465	1629	1470	1301	1465	139
15°	1381	1838	1404	862	1381	388
25°	1225	981	1251	625	1225	562
35°	1005	483	1038	461	1005	629
45°	755	336	786	329	755	583
55°	510	233	537	230	510	459
65°	308	121	327	137	308	306
75°	144	64	158	73	144	156
85°	32	18	35	19	32	36
90°	1	39	1	39	1	6
95°	60	71	60	71	60	67
105°	248	256	248	256	248	261
115°	460	460	460	460	460	455
125°	670	672	670	672	670	599
135°	867	877	867	877	867	670
145°	1052	1064	1052	1064	1052	657
155°	1203	1212	1203	1212	1203	554
165°	1309	1310	1309	1310	1309	369
175°	1362	1357	1362	1357	1362	129
180°	1364	1364	1364	1364	1364	

TEST NUMBER: P1010099

CATALOG NUMBER: S122RDIP-B675D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1473.2	1479.3	1482.3	1486.4	1495.6	1501.7	1510.8	1512.8	1511.8	1515.9	1504.7
5°	1465.0	1478.3	1490.5	1500.6	1516.9	1527.1	1538.3	1551.5	1554.6	1569.8	1560.7
7.5°	1453.8	1473.2	1490.5	1510.8	1535.2	1548.5	1565.8	1586.1	1595.3	1613.6	1618.7
10°	1435.5	1463.0	1492.5	1513.9	1547.4	1570.8	1587.1	1619.7	1641.0	1668.5	1664.4
12.5°	1406.0	1441.6	1481.3	1516.9	1560.7	1575.9	1606.4	1640.0	1667.5	1692.9	1715.3
15°	1380.6	1421.3	1465.0	1508.8	1558.6	1587.1	1617.6	1661.4	1690.9	1735.7	1755.0
17.5°	1346.0	1397.9	1449.8	1498.6	1557.6	1590.2	1627.8	1670.5	1714.3	1757.0	1772.3
20°	1310.4	1366.3	1422.3	1488.4	1555.6	1587.1	1625.8	1678.7	1721.4	1755.0	1755.0
22.5°	1267.7	1335.8	1399.9	1463.0	1536.2	1582.0	1621.7	1683.8	1714.3	1721.4	1693.9
25°	1224.9	1293.1	1363.3	1441.6	1525.1	1565.8	1610.5	1668.5	1678.7	1650.2	1579.0
27.5°	1174.1	1250.4	1329.7	1414.2	1501.7	1552.5	1593.2	1631.9	1612.6	1536.2	1425.4
30°	1122.2	1204.6	1294.1	1374.5	1480.3	1527.1	1561.7	1572.9	1511.8	1387.7	1244.3
32.5°	1068.3	1148.6	1243.2	1339.9	1446.7	1491.5	1513.9	1484.4	1372.5	1215.8	1040.8
35°	1005.2	1095.7	1194.4	1295.1	1400.9	1434.5	1447.7	1375.5	1232.1	1029.6	855.6
37.5°	948.2	1038.7	1144.6	1247.3	1350.1	1368.4	1355.2	1242.2	1060.1	859.7	689.8
40°	881.1	977.7	1081.5	1196.4	1280.9	1286.0	1253.4	1106.9	881.1	692.8	588.0
42.5°	819.0	916.7	1020.4	1137.4	1201.5	1184.2	1140.5	948.2	735.6	597.2	512.8
45°	754.9	847.5	959.4	1063.2	1108.9	1068.3	1002.1	797.6	617.6	513.8	448.7
47.5°	692.8	779.3	890.2	989.9	998.1	952.3	873.9	668.4	535.1	451.7	398.8
50°	631.8	718.3	822.0	904.5	896.3	833.2	744.7	580.9	464.9	398.8	355.1
52.5°	570.8	649.1	749.8	814.9	780.3	719.3	631.8	492.4	405.9	347.9	314.4
55°	509.7	583.0	669.4	723.4	668.4	598.2	536.2	422.2	352.0	305.2	279.8
57.5°	458.8	516.8	596.2	628.7	562.6	507.7	453.8	363.2	305.2	271.6	242.1
60°	402.9	455.8	520.9	540.2	472.1	427.3	381.5	307.2	261.5	232.0	212.6
62.5°	355.1	398.8	448.7	448.7	388.6	355.1	320.5	257.4	219.8	196.4	187.2
65°	308.3	339.8	375.4	371.3	320.5	291.0	263.5	212.6	184.1	167.9	158.7
67.5°	262.5	286.9	310.3	296.1	259.4	234.0	208.6	171.9	152.6	141.4	129.2
70°	220.8	240.1	252.3	239.1	202.5	181.1	162.8	138.4	123.1	108.9	101.7
72.5°	185.2	193.3	197.4	181.1	150.6	138.4	125.1	107.8	94.6	87.5	85.5
75°	144.5	151.6	148.5	136.3	110.9	101.7	91.6	79.4	76.3	72.2	70.2
77.5°	112.9	112.9	107.8	96.7	79.4	72.2	68.2	62.1	59.0	58.0	56.0
80°	80.4	79.4	76.3	64.1	53.9	49.9	49.9	45.8	44.8	42.7	42.7
82.5°	52.9	52.9	48.8	38.7	35.6	34.6	33.6	31.5	31.5	30.5	30.5
85°	31.5	29.5	24.4	21.4	20.3	20.3	19.3	18.3	19.3	18.3	18.3
87.5°	14.2	11.2	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
90°	1.2	4.3	7.3	10.4	13.5	15.0	17.8	23.4	29.1	34.7	40.3
92.5°	25.3	27.3	29.4	31.4	33.5	34.5	34.6	34.9	35.2	35.4	35.7
95°	59.8	62.4	65.0	67.5	70.1	71.4	71.7	72.2	72.7	73.2	73.7
97.5°	100.1	102.4	104.7	107.0	109.3	110.5	111.0	112.0	113.1	114.1	115.1
100°	146.2	148.2	150.3	152.3	154.4	155.4	155.8	156.5	157.3	158.0	158.8
102.5°	194.5	196.0	197.6	199.1	200.6	201.4	201.9	202.9	204.0	205.0	206.0
105°	247.5	248.3	249.0	249.8	250.5	250.9	251.2	251.7	252.2	252.7	253.2
107.5°	300.4	301.4	302.4	303.5	304.5	305.0	305.0	305.0	305.0	305.0	305.0
110°	351.0	352.5	354.1	355.6	357.1	357.9	357.9	357.9	357.9	357.9	357.9

TEST NUMBER: P1010099

CATALOG NUMBER: S122RDIP-B675D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	406.3	407.8	409.4	410.9	412.4	413.2	413.1	412.8	412.5	412.3	412.0
115°	460.4	461.9	463.5	465.0	466.5	467.3	467.0	466.5	466.0	465.5	465.0
117.5°	514.5	516.5	518.6	520.6	522.7	523.7	523.1	521.8	520.5	519.2	517.9
120°	568.6	570.6	572.7	574.7	576.8	577.8	576.8	574.7	572.7	570.6	568.6
122.5°	618.1	620.7	623.2	625.8	628.3	629.6	629.0	627.7	626.4	625.1	623.8
125°	669.8	672.1	674.4	676.7	679.0	680.2	679.8	679.1	678.3	677.6	676.8
127.5°	720.5	723.3	726.1	729.0	731.8	733.2	732.7	731.6	730.6	729.5	728.5
130°	767.7	771.0	774.3	777.6	780.9	782.6	782.3	781.8	781.3	780.8	780.3
132.5°	820.6	823.2	825.7	828.3	830.8	832.1	832.2	832.5	832.8	833.0	833.3
135°	866.7	869.5	872.3	875.1	877.9	879.3	879.6	880.1	880.6	881.1	881.6
137.5°	917.3	919.6	921.9	924.2	926.5	927.7	928.0	928.5	929.0	929.5	930.0
140°	962.2	964.5	966.8	969.1	971.4	972.5	973.1	974.4	975.7	977.0	978.3
142.5°	1008.2	1010.5	1012.8	1015.1	1017.4	1018.6	1019.0	1019.7	1020.5	1021.2	1022.0
145°	1052.0	1053.8	1055.6	1057.3	1059.1	1060.0	1060.8	1062.3	1063.8	1065.4	1066.9
147.5°	1091.1	1093.4	1095.7	1098.0	1100.3	1101.5	1102.0	1103.0	1104.1	1105.1	1106.1
150°	1131.4	1132.9	1134.5	1136.0	1137.5	1138.3	1138.8	1139.8	1140.9	1141.9	1142.9
152.5°	1167.1	1168.6	1170.2	1171.7	1173.2	1174.0	1174.6	1175.9	1177.2	1178.4	1179.7
155°	1202.7	1203.5	1204.3	1205.0	1205.8	1206.2	1206.6	1207.3	1208.1	1208.8	1209.6
157.5°	1233.8	1234.3	1234.8	1235.3	1235.8	1236.1	1236.4	1236.9	1237.4	1237.9	1238.4
160°	1261.4	1261.9	1262.4	1262.9	1263.4	1263.7	1263.8	1264.1	1264.4	1264.6	1264.9
162.5°	1286.8	1286.8	1286.8	1286.8	1286.8	1286.8	1286.9	1287.2	1287.4	1287.7	1287.9
165°	1308.6	1308.4	1308.1	1307.9	1307.6	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5
167.5°	1328.2	1327.4	1326.6	1325.9	1325.1	1324.7	1324.7	1324.7	1324.7	1324.7	1324.7
170°	1343.2	1342.4	1341.6	1340.9	1340.1	1339.7	1339.6	1339.3	1339.0	1338.8	1338.5
172.5°	1353.5	1352.7	1352.0	1351.2	1350.5	1350.1	1350.0	1349.7	1349.4	1349.2	1348.9
175°	1361.6	1360.8	1360.0	1359.3	1358.5	1358.1	1357.8	1357.3	1356.8	1356.3	1355.8
177.5°	1366.2	1365.4	1364.6	1363.9	1363.1	1362.7	1362.4	1361.9	1361.4	1360.9	1360.4
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P1010099

CATALOG NUMBER: S122RDIP-B675D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1515.9	1517.9	1521.0	1535.2	1537.3	1541.3	1539.3	1539.3	1540.3	1538.3	1539.3
5°	1581.0	1584.1	1599.3	1616.6	1620.7	1616.6	1621.7	1628.8	1628.8	1628.8	1626.8
7.5°	1642.1	1653.2	1670.5	1696.0	1701.1	1706.2	1715.3	1709.2	1711.2	1720.4	1717.3
10°	1701.1	1717.3	1736.7	1758.0	1769.2	1776.4	1780.4	1789.6	1810.9	1786.5	1795.7
12.5°	1757.0	1780.4	1800.8	1824.2	1832.3	1841.5	1844.5	1852.7	1852.7	1851.6	1858.8
15°	1793.6	1815.0	1833.3	1848.6	1850.6	1848.6	1846.6	1847.6	1850.6	1838.4	1845.5
17.5°	1801.8	1803.8	1809.9	1803.8	1804.8	1783.5	1771.3	1768.2	1739.7	1740.7	1764.1
20°	1762.1	1727.5	1718.4	1684.8	1664.4	1609.5	1607.5	1592.2	1532.2	1550.5	1546.4
22.5°	1653.2	1594.2	1515.9	1477.2	1457.9	1399.9	1355.2	1323.6	1302.3	1280.9	1271.7
25°	1509.8	1414.2	1303.3	1227.0	1215.8	1161.9	1079.4	1040.8	995.0	980.8	1005.2
27.5°	1324.6	1200.5	1075.4	958.4	937.0	888.2	846.5	819.0	766.1	763.0	765.1
30°	1073.3	948.2	843.4	767.1	714.2	691.8	664.4	644.0	622.6	630.8	632.8
32.5°	882.1	763.0	665.4	624.7	600.3	586.0	562.6	549.4	540.2	537.2	536.2
35°	701.0	621.6	577.9	538.2	524.0	513.8	496.5	490.4	482.2	483.3	483.3
37.5°	600.3	534.1	501.6	481.2	468.0	462.9	451.7	445.6	440.5	438.5	441.5
40°	517.8	472.1	451.7	433.4	422.2	420.2	414.1	407.0	400.8	401.9	404.9
42.5°	457.8	431.4	407.0	392.7	384.6	381.5	376.4	371.3	371.3	368.3	367.3
45°	410.0	388.6	368.3	355.1	350.0	345.9	339.8	338.8	334.7	335.7	336.8
47.5°	367.3	350.0	334.7	321.5	316.4	315.4	309.3	305.2	305.2	304.2	303.2
50°	328.6	311.3	298.1	291.0	283.9	281.8	280.8	279.8	277.7	277.7	278.8
52.5°	297.1	279.8	269.6	263.5	259.4	257.4	257.4	256.4	256.4	256.4	255.4
55°	262.5	248.2	240.1	238.1	236.0	235.0	234.0	232.0	230.9	233.0	230.9
57.5°	229.9	224.8	217.7	215.7	210.6	210.6	207.5	205.5	203.5	205.5	205.5
60°	204.5	197.4	193.3	187.2	183.1	179.1	174.0	173.0	170.9	169.9	168.9
62.5°	178.0	171.9	161.8	152.6	146.5	142.4	140.4	139.4	139.4	138.4	138.4
65°	148.5	134.3	129.2	126.2	125.1	124.1	122.1	121.1	122.1	121.1	122.1
67.5°	116.0	113.9	110.9	108.9	107.8	106.8	106.8	105.8	105.8	105.8	105.8
70°	100.7	95.6	94.6	92.6	92.6	91.6	91.6	91.6	91.6	90.5	92.6
72.5°	83.4	80.4	79.4	78.3	78.3	78.3	77.3	77.3	77.3	76.3	77.3
75°	68.2	67.1	65.1	65.1	64.1	65.1	64.1	64.1	63.1	64.1	64.1
77.5°	54.9	53.9	52.9	52.9	51.9	51.9	51.9	51.9	51.9	51.9	52.9
80°	41.7	40.7	39.7	40.7	39.7	40.7	39.7	39.7	40.7	39.7	39.7
82.5°	30.5	29.5	29.5	28.5	28.5	28.5	28.5	28.5	28.5	28.5	28.5
85°	18.3	17.3	17.3	18.3	17.3	18.3	17.3	17.3	17.3	18.3	18.3
87.5°	8.1	9.2	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	9.2
90°	39.8	39.3	38.8	38.3	38.0	38.1	38.4	38.6	38.9	39.1	38.9
92.5°	35.9	36.2	36.4	36.7	36.8	36.8	36.8	36.8	36.8	36.8	36.8
95°	73.7	73.7	73.7	73.7	73.7	73.4	72.9	72.4	71.9	71.4	71.9
97.5°	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1
100°	158.8	158.8	158.8	158.8	158.8	158.7	158.4	158.2	157.9	157.7	157.9
102.5°	206.3	206.5	206.8	207.1	207.2	207.1	206.8	206.5	206.3	206.0	206.3
105°	253.7	254.2	254.7	255.2	255.5	255.5	255.5	255.5	255.5	255.5	255.5
107.5°	305.3	305.5	305.8	306.1	306.2	305.6	304.3	303.0	301.7	300.4	301.7
110°	357.9	357.9	357.9	357.9	357.9	357.5	356.8	356.0	355.3	354.5	355.3

TEST NUMBER: P1010099

CATALOG NUMBER: S122RDIP-B675D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	411.2	410.5	409.7	409.0	408.6	408.3	407.8	407.3	406.8	406.3	406.8
115°	464.7	464.5	464.2	463.9	463.8	463.4	462.7	461.9	461.2	460.4	461.2
117.5°	517.1	516.4	515.6	514.9	514.5	514.1	513.3	512.6	511.8	511.0	511.8
120°	568.6	568.6	568.6	568.6	568.6	568.2	567.4	566.7	565.9	565.1	565.9
122.5°	623.0	622.3	621.5	620.8	620.4	620.1	619.6	619.1	618.6	618.1	618.6
125°	676.0	675.2	674.5	673.7	673.3	673.2	672.9	672.7	672.4	672.2	672.4
127.5°	727.5	726.5	725.4	724.4	723.9	723.5	722.8	722.0	721.3	720.5	721.3
130°	779.8	779.3	778.8	778.3	778.0	777.5	776.5	775.4	774.4	773.4	774.4
132.5°	832.0	830.7	829.4	828.1	827.5	827.1	826.4	825.6	824.9	824.1	824.9
135°	881.4	881.1	880.9	880.6	880.5	880.1	879.3	878.6	877.8	877.0	877.8
137.5°	929.7	929.5	929.2	928.9	928.8	928.3	927.3	926.2	925.2	924.2	925.2
140°	978.3	978.3	978.3	978.3	978.3	977.8	976.8	975.7	974.7	973.7	974.7
142.5°	1022.3	1022.5	1022.8	1023.1	1023.2	1022.7	1021.7	1020.6	1019.6	1018.6	1019.6
145°	1067.2	1067.4	1067.7	1068.0	1068.1	1067.6	1066.6	1065.5	1064.5	1063.5	1064.5
147.5°	1106.6	1107.1	1107.6	1108.1	1108.4	1107.9	1106.9	1105.8	1104.8	1103.8	1104.8
150°	1143.7	1144.4	1145.2	1145.9	1146.3	1145.9	1145.2	1144.4	1143.7	1142.9	1143.7
152.5°	1180.7	1181.7	1182.8	1183.8	1184.3	1183.8	1182.8	1181.7	1180.7	1179.7	1180.7
155°	1210.9	1212.2	1213.5	1214.8	1215.4	1215.0	1214.2	1213.5	1212.7	1211.9	1212.7
157.5°	1240.2	1242.0	1243.8	1245.6	1246.5	1245.9	1244.6	1243.3	1242.0	1240.7	1242.0
160°	1266.4	1268.0	1269.5	1271.0	1271.8	1271.3	1270.3	1269.2	1268.2	1267.2	1268.2
162.5°	1289.7	1291.5	1293.3	1295.1	1296.0	1295.4	1294.1	1292.8	1291.5	1290.2	1291.5
165°	1309.3	1311.1	1312.8	1314.6	1315.5	1314.9	1313.6	1312.3	1311.1	1309.8	1311.1
167.5°	1326.5	1328.3	1330.1	1331.9	1332.8	1332.2	1330.9	1329.6	1328.3	1327.0	1328.3
170°	1340.3	1342.1	1343.9	1345.7	1346.6	1345.8	1344.3	1342.8	1341.2	1339.7	1341.2
172.5°	1350.7	1352.5	1354.3	1356.1	1357.0	1356.2	1354.7	1353.2	1351.6	1350.1	1351.6
175°	1357.6	1359.4	1361.2	1363.0	1363.9	1363.1	1361.6	1360.1	1358.5	1357.0	1358.5
177.5°	1361.9	1363.5	1365.0	1366.5	1367.3	1366.5	1365.0	1363.5	1361.9	1360.4	1361.9
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P1010099

CATALOG NUMBER: S122RDIP-B675D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1543.4	1536.2	1534.2	1536.2	1534.2	1535.2	1528.1	1501.7	1508.8	1497.6	1503.7
5°	1630.9	1624.8	1611.5	1609.5	1607.5	1605.4	1595.3	1571.9	1562.7	1547.4	1546.4
7.5°	1714.3	1714.3	1704.1	1697.0	1687.8	1680.7	1667.5	1632.9	1618.7	1600.3	1590.2
10°	1796.7	1770.2	1781.4	1774.3	1751.9	1747.9	1723.4	1703.1	1675.6	1657.3	1641.0
12.5°	1855.7	1847.6	1837.4	1831.3	1825.2	1812.0	1795.7	1743.8	1729.6	1692.9	1674.6
15°	1853.7	1848.6	1851.6	1851.6	1849.6	1846.6	1833.3	1795.7	1771.3	1735.7	1704.1
17.5°	1754.0	1767.2	1780.4	1789.6	1809.9	1819.1	1831.3	1808.9	1793.6	1763.1	1729.6
20°	1580.0	1612.6	1651.2	1659.4	1677.7	1731.6	1756.0	1775.3	1781.4	1771.3	1743.8
22.5°	1337.9	1365.3	1458.9	1456.9	1483.3	1547.4	1618.7	1676.6	1722.4	1747.9	1737.7
25°	1047.9	1086.6	1136.4	1174.1	1260.5	1356.2	1444.7	1537.3	1616.6	1686.8	1704.1
27.5°	792.5	843.4	883.1	932.9	976.7	1089.6	1203.6	1348.0	1440.6	1573.9	1643.1
30°	641.0	664.4	704.0	727.4	748.8	835.3	964.5	1106.9	1269.7	1423.3	1542.4
32.5°	547.4	563.6	593.1	603.3	625.7	683.7	765.1	895.3	1063.2	1249.3	1406.0
35°	491.4	508.7	514.8	524.0	542.3	578.9	634.8	729.5	881.1	1063.2	1250.4
37.5°	443.6	452.7	470.0	476.1	482.2	509.7	547.4	613.5	714.2	863.8	1071.3
40°	410.0	415.1	424.2	429.3	433.4	452.7	486.3	531.1	605.3	719.3	910.6
42.5°	374.4	380.5	386.6	392.7	397.8	413.1	433.4	476.1	526.0	612.5	750.8
45°	339.8	343.9	351.0	355.1	362.2	374.4	392.7	422.2	467.0	521.9	633.8
47.5°	308.3	313.4	316.4	321.5	326.6	339.8	357.1	376.4	413.1	467.0	548.4
50°	279.8	285.9	290.0	291.0	295.0	307.2	321.5	342.9	366.3	408.0	479.2
52.5°	259.4	260.5	263.5	267.6	266.6	273.7	286.9	303.2	327.6	361.2	413.1
55°	236.0	239.1	241.1	242.1	242.1	248.2	255.4	270.6	290.0	317.4	361.2
57.5°	206.5	209.6	215.7	217.7	220.8	223.8	226.9	237.1	253.3	279.8	315.4
60°	176.0	178.0	184.1	188.2	190.3	198.4	202.5	210.6	219.8	239.1	272.7
62.5°	141.4	143.5	146.5	150.6	154.6	166.9	177.0	185.2	192.3	205.5	233.0
65°	123.1	124.1	126.2	127.2	128.2	133.3	142.4	153.6	166.9	177.0	193.3
67.5°	106.8	107.8	108.9	110.9	111.9	112.9	117.0	120.1	133.3	147.5	159.7
70°	91.6	93.6	94.6	94.6	95.6	97.7	99.7	103.8	107.8	115.0	130.2
72.5°	77.3	78.3	80.4	80.4	80.4	82.4	84.4	86.5	88.5	92.6	98.7
75°	64.1	66.1	66.1	66.1	67.1	67.1	69.2	71.2	73.3	76.3	78.3
77.5°	52.9	52.9	52.9	52.9	53.9	53.9	54.9	57.0	58.0	59.0	61.0
80°	39.7	40.7	40.7	40.7	41.7	41.7	41.7	43.7	44.8	44.8	46.8
82.5°	29.5	29.5	29.5	30.5	29.5	30.5	30.5	31.5	30.5	31.5	32.6
85°	18.3	18.3	18.3	19.3	19.3	19.3	19.3	19.3	19.3	19.3	20.3
87.5°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	10.2	9.2	9.2
90°	38.6	38.4	38.1	38.0	38.3	38.8	39.3	39.8	40.3	34.7	29.1
92.5°	36.8	36.8	36.8	36.8	36.7	36.4	36.2	35.9	35.7	35.4	35.2
95°	72.4	72.9	73.4	73.7	73.7	73.7	73.7	73.7	73.7	73.2	72.7
97.5°	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	114.1	113.1
100°	158.2	158.4	158.7	158.8	158.8	158.8	158.8	158.8	158.8	158.0	157.3
102.5°	206.5	206.8	207.1	207.2	207.1	206.8	206.5	206.3	206.0	205.0	204.0
105°	255.5	255.5	255.5	255.5	255.2	254.7	254.2	253.7	253.2	252.7	252.2
107.5°	303.0	304.3	305.6	306.2	306.1	305.8	305.5	305.3	305.0	305.0	305.0
110°	356.0	356.8	357.5	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9

TEST NUMBER: P1010099

CATALOG NUMBER: S122RDIP-B675D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	407.3	407.8	408.3	408.6	409.0	409.7	410.5	411.2	412.0	412.3	412.5
115°	461.9	462.7	463.4	463.8	463.9	464.2	464.5	464.7	465.0	465.5	466.0
117.5°	512.6	513.3	514.1	514.5	514.9	515.6	516.4	517.1	517.9	519.2	520.5
120°	566.7	567.4	568.2	568.6	568.6	568.6	568.6	568.6	568.6	570.6	572.7
122.5°	619.1	619.6	620.1	620.4	620.8	621.5	622.3	623.0	623.8	625.1	626.4
125°	672.7	672.9	673.2	673.3	673.7	674.5	675.2	676.0	676.8	677.6	678.3
127.5°	722.0	722.8	723.5	723.9	724.4	725.4	726.5	727.5	728.5	729.5	730.6
130°	775.4	776.5	777.5	778.0	778.3	778.8	779.3	779.8	780.3	780.8	781.3
132.5°	825.6	826.4	827.1	827.5	828.1	829.4	830.7	832.0	833.3	833.0	832.8
135°	878.6	879.3	880.1	880.5	880.6	880.9	881.1	881.4	881.6	881.1	880.6
137.5°	926.2	927.3	928.3	928.8	928.9	929.2	929.5	929.7	930.0	929.5	929.0
140°	975.7	976.8	977.8	978.3	978.3	978.3	978.3	978.3	978.3	977.0	975.7
142.5°	1020.6	1021.7	1022.7	1023.2	1023.1	1022.8	1022.5	1022.3	1022.0	1021.2	1020.5
145°	1065.5	1066.6	1067.6	1068.1	1068.0	1067.7	1067.4	1067.2	1066.9	1065.4	1063.8
147.5°	1105.8	1106.9	1107.9	1108.4	1108.1	1107.6	1107.1	1106.6	1106.1	1105.1	1104.1
150°	1144.4	1145.2	1145.9	1146.3	1145.9	1145.2	1144.4	1143.7	1142.9	1141.9	1140.9
152.5°	1181.7	1182.8	1183.8	1184.3	1183.8	1182.8	1181.7	1180.7	1179.7	1178.4	1177.2
155°	1213.5	1214.2	1215.0	1215.4	1214.8	1213.5	1212.2	1210.9	1209.6	1208.8	1208.1
157.5°	1243.3	1244.6	1245.9	1246.5	1245.6	1243.8	1242.0	1240.2	1238.4	1237.9	1237.4
160°	1269.2	1270.3	1271.3	1271.8	1271.0	1269.5	1268.0	1266.4	1264.9	1264.6	1264.4
162.5°	1292.8	1294.1	1295.4	1296.0	1295.1	1293.3	1291.5	1289.7	1287.9	1287.7	1287.4
165°	1312.3	1313.6	1314.9	1315.5	1314.6	1312.8	1311.1	1309.3	1307.5	1307.5	1307.5
167.5°	1329.6	1330.9	1332.2	1332.8	1331.9	1330.1	1328.3	1326.5	1324.7	1324.7	1324.7
170°	1342.8	1344.3	1345.8	1346.6	1345.7	1343.9	1342.1	1340.3	1338.5	1338.8	1339.0
172.5°	1353.2	1354.7	1356.2	1357.0	1356.1	1354.3	1352.5	1350.7	1348.9	1349.2	1349.4
175°	1360.1	1361.6	1363.1	1363.9	1363.0	1361.2	1359.4	1357.6	1355.8	1356.3	1356.8
177.5°	1363.5	1365.0	1366.5	1367.3	1366.5	1365.0	1363.5	1361.9	1360.4	1360.9	1361.4
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P1010099

CATALOG NUMBER: S122RDIP-B675D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1494.5	1489.4	1489.4	1486.4	1486.4	1470.1	1470.1	1475.2	1469.1	1462.0	1451.8
5°	1533.2	1522.0	1519.0	1514.9	1501.7	1481.3	1473.2	1470.1	1457.9	1442.7	1425.4
7.5°	1569.8	1551.5	1542.4	1533.2	1515.9	1487.4	1471.1	1459.9	1441.6	1418.2	1395.9
10°	1605.4	1582.0	1558.6	1547.4	1523.0	1487.4	1464.0	1445.7	1419.3	1387.7	1356.2
12.5°	1638.0	1589.2	1585.1	1562.7	1527.1	1486.4	1450.8	1424.3	1390.8	1354.1	1317.5
15°	1666.5	1616.6	1592.2	1571.9	1525.1	1474.2	1436.5	1404.0	1359.2	1317.5	1272.7
17.5°	1680.7	1626.8	1610.5	1576.9	1529.1	1463.0	1412.1	1372.5	1323.6	1273.8	1222.9
20°	1695.0	1631.9	1605.4	1582.0	1516.9	1441.6	1384.7	1338.9	1285.0	1225.9	1170.0
22.5°	1702.1	1631.9	1600.3	1567.8	1504.7	1418.2	1351.1	1297.2	1234.1	1174.1	1106.9
25°	1689.9	1625.8	1588.1	1554.6	1483.3	1389.7	1312.4	1251.4	1184.2	1116.1	1047.9
27.5°	1659.4	1611.5	1567.8	1533.2	1453.8	1353.1	1271.7	1202.5	1133.4	1057.1	987.9
30°	1602.4	1581.0	1546.4	1507.8	1421.3	1320.6	1223.9	1152.7	1076.4	1000.1	927.9
32.5°	1513.9	1532.2	1509.8	1476.2	1382.6	1275.8	1173.0	1100.8	1017.4	935.0	868.8
35°	1406.0	1471.1	1458.9	1435.5	1341.9	1228.0	1125.2	1037.7	954.3	870.9	804.8
37.5°	1288.0	1386.7	1396.9	1382.6	1295.1	1179.1	1066.2	980.8	895.3	810.9	743.7
40°	1126.2	1277.8	1310.4	1316.5	1246.3	1120.1	1002.1	918.7	834.3	751.8	670.5
42.5°	977.7	1169.0	1209.7	1235.1	1184.2	1062.1	943.1	850.5	767.1	692.8	611.4
45°	838.3	1037.7	1103.9	1136.4	1114.0	996.0	872.9	786.4	710.1	642.0	563.6
47.5°	694.9	895.3	987.9	1039.8	1039.8	928.9	805.8	720.3	647.1	589.1	519.9
50°	599.2	766.1	861.7	929.9	948.2	860.7	744.7	661.3	592.1	529.0	476.1
52.5°	510.7	660.3	739.6	810.9	863.8	787.5	676.6	601.3	533.1	474.1	432.4
55°	441.5	553.5	625.7	704.0	763.0	713.2	610.4	537.2	478.2	429.3	393.7
57.5°	375.4	473.1	532.1	601.3	664.4	626.7	544.3	481.2	429.3	386.6	355.1
60°	319.5	398.8	444.6	498.5	576.9	550.4	482.2	424.2	382.5	343.9	317.4
62.5°	271.6	334.7	373.4	412.0	483.3	471.0	418.1	373.4	337.8	305.2	282.8
65°	222.8	274.7	305.2	338.8	395.8	400.8	358.1	326.6	294.0	265.5	245.2
67.5°	180.1	220.8	248.2	276.7	322.5	336.8	307.2	280.8	253.3	229.9	211.6
70°	145.5	174.0	194.3	216.7	254.3	271.6	256.4	238.1	215.7	196.4	180.1
72.5°	115.0	133.3	145.5	162.8	193.3	210.6	209.6	193.3	177.0	163.8	150.6
75°	84.4	98.7	108.9	120.1	144.5	160.7	164.8	157.7	141.4	131.2	121.1
77.5°	64.1	72.2	77.3	85.5	102.8	117.0	123.1	121.1	109.9	101.7	94.6
80°	48.8	50.9	52.9	56.0	70.2	83.4	87.5	86.5	80.4	77.3	69.2
82.5°	34.6	35.6	36.6	37.6	42.7	53.9	58.0	60.0	54.9	51.9	44.8
85°	20.3	21.4	21.4	23.4	24.4	27.5	34.6	34.6	33.6	29.5	28.5
87.5°	10.2	10.2	9.2	9.2	10.2	11.2	13.2	15.3	13.2	12.2	11.2
90°	23.4	17.8	15.0	13.5	10.4	7.3	4.3	1.2	4.3	7.3	10.4
92.5°	34.9	34.6	34.5	33.5	31.4	29.4	27.3	25.3	27.3	29.4	31.4
95°	72.2	71.7	71.4	70.1	67.5	65.0	62.4	59.8	62.4	65.0	67.5
97.5°	112.0	111.0	110.5	109.3	107.0	104.7	102.4	100.1	102.4	104.7	107.0
100°	156.5	155.8	155.4	154.4	152.3	150.3	148.2	146.2	148.2	150.3	152.3
102.5°	202.9	201.9	201.4	200.6	199.1	197.6	196.0	194.5	196.0	197.6	199.1
105°	251.7	251.2	250.9	250.5	249.8	249.0	248.3	247.5	248.3	249.0	249.8
107.5°	305.0	305.0	305.0	304.5	303.5	302.4	301.4	300.4	301.4	302.4	303.5
110°	357.9	357.9	357.9	357.1	355.6	354.1	352.5	351.0	352.5	354.1	355.6

TEST NUMBER: P1010099

CATALOG NUMBER: S122RDIP-B675D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	412.8	413.1	413.2	412.4	410.9	409.4	407.8	406.3	407.8	409.4	410.9
115°	466.5	467.0	467.3	466.5	465.0	463.5	461.9	460.4	461.9	463.5	465.0
117.5°	521.8	523.1	523.7	522.7	520.6	518.6	516.5	514.5	516.5	518.6	520.6
120°	574.7	576.8	577.8	576.8	574.7	572.7	570.6	568.6	570.6	572.7	574.7
122.5°	627.7	629.0	629.6	628.3	625.8	623.2	620.7	618.1	620.7	623.2	625.8
125°	679.1	679.8	680.2	679.0	676.7	674.4	672.1	669.8	672.1	674.4	676.7
127.5°	731.6	732.7	733.2	731.8	729.0	726.1	723.3	720.5	723.3	726.1	729.0
130°	781.8	782.3	782.6	780.9	777.6	774.3	771.0	767.7	771.0	774.3	777.6
132.5°	832.5	832.2	832.1	830.8	828.3	825.7	823.2	820.6	823.2	825.7	828.3
135°	880.1	879.6	879.3	877.9	875.1	872.3	869.5	866.7	869.5	872.3	875.1
137.5°	928.5	928.0	927.7	926.5	924.2	921.9	919.6	917.3	919.6	921.9	924.2
140°	974.4	973.1	972.5	971.4	969.1	966.8	964.5	962.2	964.5	966.8	969.1
142.5°	1019.7	1019.0	1018.6	1017.4	1015.1	1012.8	1010.5	1008.2	1010.5	1012.8	1015.1
145°	1062.3	1060.8	1060.0	1059.1	1057.3	1055.6	1053.8	1052.0	1053.8	1055.6	1057.3
147.5°	1103.0	1102.0	1101.5	1100.3	1098.0	1095.7	1093.4	1091.1	1093.4	1095.7	1098.0
150°	1139.8	1138.8	1138.3	1137.5	1136.0	1134.5	1132.9	1131.4	1132.9	1134.5	1136.0
152.5°	1175.9	1174.6	1174.0	1173.2	1171.7	1170.2	1168.6	1167.1	1168.6	1170.2	1171.7
155°	1207.3	1206.6	1206.2	1205.8	1205.0	1204.3	1203.5	1202.7	1203.5	1204.3	1205.0
157.5°	1236.9	1236.4	1236.1	1235.8	1235.3	1234.8	1234.3	1233.8	1234.3	1234.8	1235.3
160°	1264.1	1263.8	1263.7	1263.4	1262.9	1262.4	1261.9	1261.4	1261.9	1262.4	1262.9
162.5°	1287.2	1286.9	1286.8	1286.8	1286.8	1286.8	1286.8	1286.8	1286.8	1286.8	1286.8
165°	1307.5	1307.5	1307.5	1307.6	1307.9	1308.1	1308.4	1308.6	1308.4	1308.1	1307.9
167.5°	1324.7	1324.7	1324.7	1325.1	1325.9	1326.6	1327.4	1328.2	1327.4	1326.6	1325.9
170°	1339.3	1339.6	1339.7	1340.1	1340.9	1341.6	1342.4	1343.2	1342.4	1341.6	1340.9
172.5°	1349.7	1350.0	1350.1	1350.5	1351.2	1352.0	1352.7	1353.5	1352.7	1352.0	1351.2
175°	1357.3	1357.8	1358.1	1358.5	1359.3	1360.0	1360.8	1361.6	1360.8	1360.0	1359.3
177.5°	1361.9	1362.4	1362.7	1363.1	1363.9	1364.6	1365.4	1366.2	1365.4	1364.6	1363.9
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P1010099

CATALOG NUMBER: S122RDIP-B675D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1447.7	1448.8	1451.8	1442.7	1428.4	1422.3	1404.0	1400.9	1397.9	1397.9	1400.9
5°	1415.2	1411.1	1412.1	1394.8	1374.5	1362.3	1336.8	1340.9	1327.7	1319.5	1321.6
7.5°	1379.6	1368.4	1367.4	1345.0	1319.5	1297.2	1270.7	1264.6	1252.4	1238.2	1232.1
10°	1334.8	1326.7	1311.4	1286.0	1253.4	1235.1	1199.5	1178.1	1175.1	1153.7	1145.6
12.5°	1289.0	1274.8	1259.5	1223.9	1187.3	1157.8	1131.3	1107.9	1091.7	1073.3	1061.1
15°	1236.1	1218.8	1201.5	1163.9	1121.2	1091.7	1052.0	1017.4	969.6	931.9	910.6
17.5°	1178.1	1158.8	1135.4	1093.7	1052.0	1011.3	938.0	897.3	863.8	841.4	828.2
20°	1118.1	1096.7	1073.3	1031.6	959.4	888.2	847.5	815.9	795.6	773.2	756.9
22.5°	1055.0	1032.6	1007.2	942.1	865.8	815.9	784.4	754.9	725.4	713.2	705.0
25°	996.0	975.7	943.1	854.6	794.6	748.8	713.2	693.9	678.6	662.3	647.1
27.5°	935.0	897.3	851.6	777.3	739.6	692.8	667.4	653.2	626.7	615.5	608.4
30°	861.7	820.0	776.3	723.4	679.6	647.1	623.7	600.3	585.0	573.8	561.6
32.5°	787.5	747.8	720.3	665.4	632.8	599.2	576.9	562.6	540.2	533.1	528.0
35°	723.4	689.8	665.4	620.6	590.1	559.6	543.3	521.9	507.7	494.4	486.3
37.5°	660.3	642.0	616.5	578.9	546.3	521.9	499.5	492.4	473.1	466.0	457.8
40°	616.5	589.1	567.7	535.1	507.7	481.2	467.0	450.7	437.5	426.3	423.2
42.5°	563.6	543.3	531.1	495.5	467.0	451.7	434.4	416.1	405.9	396.8	385.6
45°	524.0	505.6	488.3	459.9	434.4	415.1	399.8	387.6	370.3	366.3	349.0
47.5°	482.2	463.9	450.7	422.2	398.8	380.5	369.3	353.0	338.8	329.6	321.5
50°	440.5	425.3	413.1	388.6	368.3	349.0	333.7	317.4	311.3	296.1	291.0
52.5°	400.8	390.7	377.4	354.0	333.7	317.4	301.1	287.9	278.8	270.6	264.5
55°	367.3	351.0	344.9	319.5	302.2	284.9	270.6	262.5	251.3	246.2	241.1
57.5°	329.6	320.5	310.3	291.0	271.6	255.4	245.2	233.0	226.9	220.8	216.7
60°	297.1	283.9	275.7	259.4	242.1	226.9	217.7	208.6	200.4	195.3	187.2
62.5°	259.4	249.3	244.2	226.9	212.6	198.4	190.3	181.1	175.0	165.8	155.7
65°	226.9	218.7	212.6	198.4	185.2	171.9	163.8	152.6	144.5	139.4	138.4
67.5°	198.4	192.3	183.1	169.9	156.7	146.5	137.3	128.2	127.2	125.1	125.1
70°	166.9	160.7	155.7	141.4	130.2	119.0	117.0	113.9	110.9	109.9	107.8
72.5°	139.4	134.3	128.2	116.0	104.8	101.7	99.7	97.7	94.6	93.6	92.6
75°	112.9	105.8	101.7	90.5	87.5	85.5	83.4	80.4	78.3	77.3	75.3
77.5°	86.5	79.4	79.4	73.3	71.2	68.2	66.1	64.1	63.1	61.0	61.0
80°	61.0	61.0	59.0	56.0	52.9	51.9	48.8	47.8	46.8	47.8	45.8
82.5°	44.8	40.7	40.7	38.7	36.6	35.6	33.6	33.6	32.6	32.6	32.6
85°	25.4	25.4	24.4	22.4	21.4	21.4	20.3	20.3	19.3	19.3	18.3
87.5°	10.2	9.2	10.2	9.2	9.2	8.1	8.1	8.1	7.1	8.1	7.1
90°	13.5	15.0	17.8	23.4	29.1	34.7	40.3	39.8	39.3	38.8	38.3
92.5°	33.5	34.5	34.6	34.9	35.2	35.4	35.7	35.9	36.2	36.4	36.7
95°	70.1	71.4	71.7	72.2	72.7	73.2	73.7	73.7	73.7	73.7	73.7
97.5°	109.3	110.5	111.0	112.0	113.1	114.1	115.1	115.1	115.1	115.1	115.1
100°	154.4	155.4	155.8	156.5	157.3	158.0	158.8	158.8	158.8	158.8	158.8
102.5°	200.6	201.4	201.9	202.9	204.0	205.0	206.0	206.3	206.5	206.8	207.1
105°	250.5	250.9	251.2	251.7	252.2	252.7	253.2	253.7	254.2	254.7	255.2
107.5°	304.5	305.0	305.0	305.0	305.0	305.0	305.0	305.3	305.5	305.8	306.1
110°	357.1	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9

TEST NUMBER: P1010099

CATALOG NUMBER: S122RDIP-B675D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	412.4	413.2	413.1	412.8	412.5	412.3	412.0	411.2	410.5	409.7	409.0
115°	466.5	467.3	467.0	466.5	466.0	465.5	465.0	464.7	464.5	464.2	463.9
117.5°	522.7	523.7	523.1	521.8	520.5	519.2	517.9	517.1	516.4	515.6	514.9
120°	576.8	577.8	576.8	574.7	572.7	570.6	568.6	568.6	568.6	568.6	568.6
122.5°	628.3	629.6	629.0	627.7	626.4	625.1	623.8	623.0	622.3	621.5	620.8
125°	679.0	680.2	679.8	679.1	678.3	677.6	676.8	676.0	675.2	674.5	673.7
127.5°	731.8	733.2	732.7	731.6	730.6	729.5	728.5	727.5	726.5	725.4	724.4
130°	780.9	782.6	782.3	781.8	781.3	780.8	780.3	779.8	779.3	778.8	778.3
132.5°	830.8	832.1	832.2	832.5	832.8	833.0	833.3	832.0	830.7	829.4	828.1
135°	877.9	879.3	879.6	880.1	880.6	881.1	881.6	881.4	881.1	880.9	880.6
137.5°	926.5	927.7	928.0	928.5	929.0	929.5	930.0	929.7	929.5	929.2	928.9
140°	971.4	972.5	973.1	974.4	975.7	977.0	978.3	978.3	978.3	978.3	978.3
142.5°	1017.4	1018.6	1019.0	1019.7	1020.5	1021.2	1022.0	1022.3	1022.5	1022.8	1023.1
145°	1059.1	1060.0	1060.8	1062.3	1063.8	1065.4	1066.9	1067.2	1067.4	1067.7	1068.0
147.5°	1100.3	1101.5	1102.0	1103.0	1104.1	1105.1	1106.1	1106.6	1107.1	1107.6	1108.1
150°	1137.5	1138.3	1138.8	1139.8	1140.9	1141.9	1142.9	1143.7	1144.4	1145.2	1145.9
152.5°	1173.2	1174.0	1174.6	1175.9	1177.2	1178.4	1179.7	1180.7	1181.7	1182.8	1183.8
155°	1205.8	1206.2	1206.6	1207.3	1208.1	1208.8	1209.6	1210.9	1212.2	1213.5	1214.8
157.5°	1235.8	1236.1	1236.4	1236.9	1237.4	1237.9	1238.4	1240.2	1242.0	1243.8	1245.6
160°	1263.4	1263.7	1263.8	1264.1	1264.4	1264.6	1264.9	1266.4	1268.0	1269.5	1271.0
162.5°	1286.8	1286.8	1286.9	1287.2	1287.4	1287.7	1287.9	1289.7	1291.5	1293.3	1295.1
165°	1307.6	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1309.3	1311.1	1312.8	1314.6
167.5°	1325.1	1324.7	1324.7	1324.7	1324.7	1324.7	1324.7	1326.5	1328.3	1330.1	1331.9
170°	1340.1	1339.7	1339.6	1339.3	1339.0	1338.8	1338.5	1340.3	1342.1	1343.9	1345.7
172.5°	1350.5	1350.1	1350.0	1349.7	1349.4	1349.2	1348.9	1350.7	1352.5	1354.3	1356.1
175°	1358.5	1358.1	1357.8	1357.3	1356.8	1356.3	1355.8	1357.6	1359.4	1361.2	1363.0
177.5°	1363.1	1362.7	1362.4	1361.9	1361.4	1360.9	1360.4	1361.9	1363.5	1365.0	1366.5
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P1010099

CATALOG NUMBER: S122RDIP-B675D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1400.9	1398.9	1392.8	1394.8	1391.8	1391.8	1389.7	1389.7	1389.7	1394.8	1391.8
5°	1324.6	1317.5	1310.4	1307.3	1304.3	1301.2	1301.2	1300.2	1309.4	1307.3	1315.5
7.5°	1230.0	1228.0	1213.7	1213.7	1208.7	1206.6	1211.7	1212.7	1213.7	1215.8	1220.9
10°	1145.6	1140.5	1120.1	1122.2	1119.1	1115.1	1118.1	1116.1	1123.2	1125.2	1123.2
12.5°	1045.9	1036.7	1014.3	1003.1	990.9	981.8	993.0	984.8	1013.3	1021.5	1043.8
15°	913.6	896.3	881.1	881.1	869.9	861.7	866.8	876.0	882.1	891.2	895.3
17.5°	825.1	818.0	805.8	798.6	795.6	792.5	792.5	796.6	809.8	808.8	817.0
20°	749.8	745.7	739.6	730.5	727.4	725.4	725.4	725.4	734.6	742.7	747.8
22.5°	697.9	694.9	690.8	678.6	672.5	670.5	675.5	678.6	685.7	691.8	696.9
25°	646.0	638.9	631.8	627.7	624.7	624.7	626.7	627.7	630.8	633.8	639.9
27.5°	603.3	598.2	588.0	576.9	576.9	573.8	575.8	577.9	585.0	595.2	600.3
30°	555.5	554.5	550.4	546.3	542.3	540.2	544.3	547.4	548.4	553.5	553.5
32.5°	520.9	513.8	506.7	502.6	500.6	499.5	500.6	504.6	504.6	510.7	517.8
35°	486.3	482.2	475.1	468.0	466.0	460.9	464.9	469.0	476.1	479.2	482.2
37.5°	448.7	443.6	440.5	438.5	434.4	435.4	432.4	438.5	444.6	443.6	445.6
40°	420.2	411.0	401.9	400.8	399.8	398.8	398.8	399.8	403.9	408.0	414.1
42.5°	383.6	380.5	372.4	364.2	362.2	360.2	358.1	362.2	370.3	377.4	380.5
45°	345.9	341.8	339.8	333.7	329.6	328.6	326.6	331.7	338.8	341.8	343.9
47.5°	311.3	310.3	304.2	305.2	302.2	303.2	302.2	305.2	305.2	308.3	310.3
50°	287.9	284.9	281.8	279.8	276.7	276.7	275.7	276.7	280.8	284.9	283.9
52.5°	264.5	259.4	258.4	257.4	255.4	257.4	254.3	255.4	259.4	261.5	260.5
55°	237.1	236.0	234.0	232.0	230.9	229.9	229.9	229.9	234.0	237.1	238.1
57.5°	215.7	210.6	206.5	206.5	202.5	201.4	203.5	204.5	207.5	209.6	211.6
60°	186.2	184.1	178.0	175.0	168.9	167.9	167.9	171.9	177.0	184.1	186.2
62.5°	154.6	151.6	150.6	150.6	150.6	150.6	150.6	150.6	150.6	151.6	151.6
65°	137.3	138.4	137.3	136.3	137.3	137.3	136.3	136.3	136.3	137.3	138.4
67.5°	123.1	122.1	123.1	122.1	121.1	121.1	120.1	121.1	122.1	123.1	123.1
70°	106.8	106.8	105.8	106.8	105.8	104.8	103.8	103.8	105.8	106.8	106.8
72.5°	91.6	91.6	90.5	90.5	88.5	88.5	89.5	88.5	88.5	91.6	91.6
75°	76.3	75.3	74.3	74.3	73.3	73.3	73.3	72.2	74.3	74.3	75.3
77.5°	60.0	60.0	60.0	59.0	59.0	58.0	58.0	59.0	59.0	59.0	60.0
80°	45.8	45.8	45.8	44.8	43.7	43.7	43.7	43.7	43.7	44.8	43.7
82.5°	31.5	31.5	31.5	31.5	31.5	30.5	30.5	30.5	31.5	31.5	30.5
85°	19.3	18.3	19.3	19.3	18.3	19.3	18.3	18.3	17.3	17.3	18.3
87.5°	8.1	7.1	6.1	6.1	7.1	6.1	6.1	6.1	7.1	6.1	6.1
90°	38.0	38.1	38.4	38.6	38.9	39.1	38.9	38.6	38.4	38.1	38.0
92.5°	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8
95°	73.7	73.4	72.9	72.4	71.9	71.4	71.9	72.4	72.9	73.4	73.7
97.5°	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1
100°	158.8	158.7	158.4	158.2	157.9	157.7	157.9	158.2	158.4	158.7	158.8
102.5°	207.2	207.1	206.8	206.5	206.3	206.0	206.3	206.5	206.8	207.1	207.2
105°	255.5	255.5	255.5	255.5	255.5	255.5	255.5	255.5	255.5	255.5	255.5
107.5°	306.2	305.6	304.3	303.0	301.7	300.4	301.7	303.0	304.3	305.6	306.2
110°	357.9	357.5	356.8	356.0	355.3	354.5	355.3	356.0	356.8	357.5	357.9

TEST NUMBER: P1010099

CATALOG NUMBER: S122RDIP-B675D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	408.6	408.3	407.8	407.3	406.8	406.3	406.8	407.3	407.8	408.3	408.6
115°	463.8	463.4	462.7	461.9	461.2	460.4	461.2	461.9	462.7	463.4	463.8
117.5°	514.5	514.1	513.3	512.6	511.8	511.0	511.8	512.6	513.3	514.1	514.5
120°	568.6	568.2	567.4	566.7	565.9	565.1	565.9	566.7	567.4	568.2	568.6
122.5°	620.4	620.1	619.6	619.1	618.6	618.1	618.6	619.1	619.6	620.1	620.4
125°	673.3	673.2	672.9	672.7	672.4	672.2	672.4	672.7	672.9	673.2	673.3
127.5°	723.9	723.5	722.8	722.0	721.3	720.5	721.3	722.0	722.8	723.5	723.9
130°	778.0	777.5	776.5	775.4	774.4	773.4	774.4	775.4	776.5	777.5	778.0
132.5°	827.5	827.1	826.4	825.6	824.9	824.1	824.9	825.6	826.4	827.1	827.5
135°	880.5	880.1	879.3	878.6	877.8	877.0	877.8	878.6	879.3	880.1	880.5
137.5°	928.8	928.3	927.3	926.2	925.2	924.2	925.2	926.2	927.3	928.3	928.8
140°	978.3	977.8	976.8	975.7	974.7	973.7	974.7	975.7	976.8	977.8	978.3
142.5°	1023.2	1022.7	1021.7	1020.6	1019.6	1018.6	1019.6	1020.6	1021.7	1022.7	1023.2
145°	1068.1	1067.6	1066.6	1065.5	1064.5	1063.5	1064.5	1065.5	1066.6	1067.6	1068.1
147.5°	1108.4	1107.9	1106.9	1105.8	1104.8	1103.8	1104.8	1105.8	1106.9	1107.9	1108.4
150°	1146.3	1145.9	1145.2	1144.4	1143.7	1142.9	1143.7	1144.4	1145.2	1145.9	1146.3
152.5°	1184.3	1183.8	1182.8	1181.7	1180.7	1179.7	1180.7	1181.7	1182.8	1183.8	1184.3
155°	1215.4	1215.0	1214.2	1213.5	1212.7	1211.9	1212.7	1213.5	1214.2	1215.0	1215.4
157.5°	1246.5	1245.9	1244.6	1243.3	1242.0	1240.7	1242.0	1243.3	1244.6	1245.9	1246.5
160°	1271.8	1271.3	1270.3	1269.2	1268.2	1267.2	1268.2	1269.2	1270.3	1271.3	1271.8
162.5°	1296.0	1295.4	1294.1	1292.8	1291.5	1290.2	1291.5	1292.8	1294.1	1295.4	1296.0
165°	1315.5	1314.9	1313.6	1312.3	1311.1	1309.8	1311.1	1312.3	1313.6	1314.9	1315.5
167.5°	1332.8	1332.2	1330.9	1329.6	1328.3	1327.0	1328.3	1329.6	1330.9	1332.2	1332.8
170°	1346.6	1345.8	1344.3	1342.8	1341.2	1339.7	1341.2	1342.8	1344.3	1345.8	1346.6
172.5°	1357.0	1356.2	1354.7	1353.2	1351.6	1350.1	1351.6	1353.2	1354.7	1356.2	1357.0
175°	1363.9	1363.1	1361.6	1360.1	1358.5	1357.0	1358.5	1360.1	1361.6	1363.1	1363.9
177.5°	1367.3	1366.5	1365.0	1363.5	1361.9	1360.4	1361.9	1363.5	1365.0	1366.5	1367.3
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P1010099

CATALOG NUMBER: S122RDIP-B675D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1394.8	1399.9	1397.9	1386.7	1397.9	1400.9	1407.0	1413.1	1417.2	1423.3	1428.4
5°	1307.3	1317.5	1323.6	1317.5	1337.9	1340.9	1355.2	1363.3	1375.5	1385.7	1393.8
7.5°	1224.9	1233.1	1245.3	1247.3	1259.5	1273.8	1294.1	1314.5	1333.8	1344.0	1353.1
10°	1136.4	1150.7	1169.0	1164.9	1183.2	1205.6	1227.0	1259.5	1275.8	1294.1	1310.4
12.5°	1047.9	1057.1	1081.5	1089.6	1116.1	1133.4	1162.9	1183.2	1223.9	1245.3	1259.5
15°	893.3	930.9	961.4	998.1	1032.6	1065.2	1091.7	1128.3	1163.9	1180.2	1203.6
17.5°	823.1	840.4	858.7	877.0	921.7	979.7	1026.5	1066.2	1096.7	1118.1	1145.6
20°	749.8	767.1	787.5	804.8	832.2	873.9	931.9	1000.1	1036.7	1059.1	1085.5
22.5°	697.9	714.2	727.4	742.7	764.1	794.6	838.3	922.8	971.6	999.1	1022.5
25°	642.0	662.3	676.6	687.8	705.0	738.6	774.2	822.0	909.5	930.9	963.5
27.5°	603.3	609.4	625.7	643.0	660.3	678.6	715.2	755.9	814.9	861.7	901.4
30°	557.5	572.8	588.0	595.2	610.4	636.9	659.3	703.0	748.8	785.4	833.2
32.5°	522.9	532.1	542.3	559.6	573.8	592.1	614.5	651.1	689.8	713.2	749.8
35°	484.3	490.4	511.7	518.9	533.1	551.4	573.8	602.3	644.0	662.3	688.8
37.5°	447.6	461.9	468.0	484.3	497.5	515.8	532.1	564.6	592.1	613.5	637.9
40°	419.2	425.3	436.5	450.7	461.9	476.1	496.5	519.9	549.4	566.7	588.0
42.5°	384.6	389.7	403.9	412.0	430.4	443.6	455.8	484.3	510.7	524.0	545.3
45°	346.9	359.1	368.3	384.6	394.7	411.0	426.3	446.6	471.0	486.3	498.5
47.5°	314.4	326.6	335.7	351.0	367.3	374.4	390.7	412.0	434.4	446.6	463.9
50°	287.9	292.0	309.3	316.4	333.7	347.9	359.1	377.4	401.9	409.0	423.2
52.5°	262.5	265.5	276.7	285.9	301.1	313.4	327.6	344.9	365.2	376.4	387.6
55°	240.1	242.1	247.2	257.4	267.6	282.8	296.1	312.3	329.6	341.8	352.0
57.5°	214.7	218.7	222.8	228.9	239.1	253.3	267.6	282.8	297.1	305.2	318.4
60°	185.2	191.3	198.4	205.5	212.6	222.8	239.1	253.3	266.6	273.7	283.9
62.5°	153.6	165.8	171.9	180.1	186.2	195.3	207.5	223.8	233.0	242.1	250.3
65°	138.4	139.4	140.4	148.5	159.7	168.9	180.1	192.3	206.5	212.6	218.7
67.5°	123.1	124.1	126.2	127.2	131.2	141.4	153.6	166.9	178.0	182.1	188.2
70°	107.8	107.8	111.9	112.9	113.9	115.0	125.1	138.4	148.5	153.6	160.7
72.5°	91.6	92.6	94.6	95.6	97.7	99.7	102.8	109.9	122.1	127.2	135.3
75°	75.3	76.3	77.3	78.3	81.4	82.4	85.5	89.5	94.6	100.7	105.8
77.5°	60.0	60.0	61.0	63.1	65.1	66.1	69.2	71.2	73.3	76.3	80.4
80°	44.8	45.8	45.8	47.8	47.8	48.8	49.9	52.9	54.9	57.0	59.0
82.5°	30.5	32.6	32.6	32.6	33.6	34.6	35.6	35.6	37.6	38.7	41.7
85°	18.3	19.3	19.3	19.3	18.3	20.3	20.3	21.4	21.4	21.4	22.4
87.5°	7.1	6.1	7.1	7.1	7.1	8.1	7.1	7.1	8.1	9.2	9.2
90°	38.3	38.8	39.3	39.8	40.3	34.7	29.1	23.4	17.8	15.0	13.5
92.5°	36.7	36.4	36.2	35.9	35.7	35.4	35.2	34.9	34.6	34.5	33.5
95°	73.7	73.7	73.7	73.7	73.7	73.2	72.7	72.2	71.7	71.4	70.1
97.5°	115.1	115.1	115.1	115.1	115.1	114.1	113.1	112.0	111.0	110.5	109.3
100°	158.8	158.8	158.8	158.8	158.8	158.0	157.3	156.5	155.8	155.4	154.4
102.5°	207.1	206.8	206.5	206.3	206.0	205.0	204.0	202.9	201.9	201.4	200.6
105°	255.2	254.7	254.2	253.7	253.2	252.7	252.2	251.7	251.2	250.9	250.5
107.5°	306.1	305.8	305.5	305.3	305.0	305.0	305.0	305.0	305.0	305.0	304.5
110°	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.1

TEST NUMBER: P1010099

CATALOG NUMBER: S122RDIP-B675D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	409.0	409.7	410.5	411.2	412.0	412.3	412.5	412.8	413.1	413.2	412.4
115°	463.9	464.2	464.5	464.7	465.0	465.5	466.0	466.5	467.0	467.3	466.5
117.5°	514.9	515.6	516.4	517.1	517.9	519.2	520.5	521.8	523.1	523.7	522.7
120°	568.6	568.6	568.6	568.6	568.6	570.6	572.7	574.7	576.8	577.8	576.8
122.5°	620.8	621.5	622.3	623.0	623.8	625.1	626.4	627.7	629.0	629.6	628.3
125°	673.7	674.5	675.2	676.0	676.8	677.6	678.3	679.1	679.8	680.2	679.0
127.5°	724.4	725.4	726.5	727.5	728.5	729.5	730.6	731.6	732.7	733.2	731.8
130°	778.3	778.8	779.3	779.8	780.3	780.8	781.3	781.8	782.3	782.6	780.9
132.5°	828.1	829.4	830.7	832.0	833.3	833.0	832.8	832.5	832.2	832.1	830.8
135°	880.6	880.9	881.1	881.4	881.6	881.1	880.6	880.1	879.6	879.3	877.9
137.5°	928.9	929.2	929.5	929.7	930.0	929.5	929.0	928.5	928.0	927.7	926.5
140°	978.3	978.3	978.3	978.3	978.3	977.0	975.7	974.4	973.1	972.5	971.4
142.5°	1023.1	1022.8	1022.5	1022.3	1022.0	1021.2	1020.5	1019.7	1019.0	1018.6	1017.4
145°	1068.0	1067.7	1067.4	1067.2	1066.9	1065.4	1063.8	1062.3	1060.8	1060.0	1059.1
147.5°	1108.1	1107.6	1107.1	1106.6	1106.1	1105.1	1104.1	1103.0	1102.0	1101.5	1100.3
150°	1145.9	1145.2	1144.4	1143.7	1142.9	1141.9	1140.9	1139.8	1138.8	1138.3	1137.5
152.5°	1183.8	1182.8	1181.7	1180.7	1179.7	1178.4	1177.2	1175.9	1174.6	1174.0	1173.2
155°	1214.8	1213.5	1212.2	1210.9	1209.6	1208.8	1208.1	1207.3	1206.6	1206.2	1205.8
157.5°	1245.6	1243.8	1242.0	1240.2	1238.4	1237.9	1237.4	1236.9	1236.4	1236.1	1235.8
160°	1271.0	1269.5	1268.0	1266.4	1264.9	1264.6	1264.4	1264.1	1263.8	1263.7	1263.4
162.5°	1295.1	1293.3	1291.5	1289.7	1287.9	1287.7	1287.4	1287.2	1286.9	1286.8	1286.8
165°	1314.6	1312.8	1311.1	1309.3	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.6
167.5°	1331.9	1330.1	1328.3	1326.5	1324.7	1324.7	1324.7	1324.7	1324.7	1324.7	1325.1
170°	1345.7	1343.9	1342.1	1340.3	1338.5	1338.8	1339.0	1339.3	1339.6	1339.7	1340.1
172.5°	1356.1	1354.3	1352.5	1350.7	1348.9	1349.2	1349.4	1349.7	1350.0	1350.1	1350.5
175°	1363.0	1361.2	1359.4	1357.6	1355.8	1356.3	1356.8	1357.3	1357.8	1358.1	1358.5
177.5°	1366.5	1365.0	1363.5	1361.9	1360.4	1360.9	1361.4	1361.9	1362.4	1362.7	1363.1
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P1010099

CATALOG NUMBER: S122RDIP-B675D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1464.0	1464.0	1464.0	1464.0
2.5°	1437.6	1434.5	1452.8	1473.2
5°	1408.1	1413.1	1436.5	1465.0
7.5°	1377.5	1388.7	1416.2	1453.8
10°	1334.8	1355.2	1396.9	1435.5
12.5°	1293.1	1320.6	1360.2	1406.0
15°	1246.3	1276.8	1325.7	1380.6
17.5°	1194.4	1229.0	1286.0	1346.0
20°	1139.5	1185.3	1245.3	1310.4
22.5°	1078.4	1133.4	1195.4	1267.7
25°	1019.4	1079.4	1141.5	1224.9
27.5°	961.4	1020.4	1089.6	1174.1
30°	903.4	957.4	1031.6	1122.2
32.5°	841.4	897.3	975.7	1068.3
35°	784.4	840.4	913.6	1005.2
37.5°	723.4	783.4	853.6	948.2
40°	652.1	722.3	790.5	881.1
42.5°	593.1	667.4	733.5	819.0
45°	546.3	616.5	671.5	754.9
47.5°	502.6	559.6	615.5	692.8
50°	460.9	504.6	562.6	631.8
52.5°	418.1	455.8	505.6	570.8
55°	379.5	415.1	459.9	509.7
57.5°	343.9	369.3	414.1	458.8
60°	304.2	330.6	365.2	402.9
62.5°	270.6	291.0	323.5	355.1
65°	235.0	254.3	278.8	308.3
67.5°	202.5	219.8	239.1	262.5
70°	173.0	186.2	200.4	220.8
72.5°	141.4	155.7	168.9	185.2
75°	116.0	122.1	133.3	144.5
77.5°	89.5	97.7	103.8	112.9
80°	64.1	71.2	73.3	80.4
82.5°	42.7	46.8	50.9	52.9
85°	24.4	26.5	30.5	31.5
87.5°	9.2	10.2	12.2	14.2
90°	10.4	7.3	4.3	1.2
92.5°	31.4	29.4	27.3	25.3
95°	67.5	65.0	62.4	59.8
97.5°	107.0	104.7	102.4	100.1
100°	152.3	150.3	148.2	146.2
102.5°	199.1	197.6	196.0	194.5
105°	249.8	249.0	248.3	247.5
107.5°	303.5	302.4	301.4	300.4
110°	355.6	354.1	352.5	351.0

TEST NUMBER: P1010099

CATALOG NUMBER: S122RDIP-B675D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	410.9	409.4	407.8	406.3
115°	465.0	463.5	461.9	460.4
117.5°	520.6	518.6	516.5	514.5
120°	574.7	572.7	570.6	568.6
122.5°	625.8	623.2	620.7	618.1
125°	676.7	674.4	672.1	669.8
127.5°	729.0	726.1	723.3	720.5
130°	777.6	774.3	771.0	767.7
132.5°	828.3	825.7	823.2	820.6
135°	875.1	872.3	869.5	866.7
137.5°	924.2	921.9	919.6	917.3
140°	969.1	966.8	964.5	962.2
142.5°	1015.1	1012.8	1010.5	1008.2
145°	1057.3	1055.6	1053.8	1052.0
147.5°	1098.0	1095.7	1093.4	1091.1
150°	1136.0	1134.5	1132.9	1131.4
152.5°	1171.7	1170.2	1168.6	1167.1
155°	1205.0	1204.3	1203.5	1202.7
157.5°	1235.3	1234.8	1234.3	1233.8
160°	1262.9	1262.4	1261.9	1261.4
162.5°	1286.8	1286.8	1286.8	1286.8
165°	1307.9	1308.1	1308.4	1308.6
167.5°	1325.9	1326.6	1327.4	1328.2
170°	1340.9	1341.6	1342.4	1343.2
172.5°	1351.2	1352.0	1352.7	1353.5
175°	1359.3	1360.0	1360.8	1361.6
177.5°	1363.9	1364.6	1365.4	1366.2
180°	1363.9	1363.9	1363.9	1363.9

(END OF REPORT)