

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010122

Luminaire Tested: S122RDIP-B675D1080UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010122
REPORT IS A COMBINATION OF REPORTS P988454 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B675D1080UB50-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6500.0 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010122

CATALOG NUMBER: S122RDIP-B675D1080UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1010122

CATALOG NUMBER: S122RDIP-B675D1080UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	39	39	39
1	96	92	88	85	87	83	80	78	68	66	64	54	52	51	41	40	39	33	33	33
2	88	81	75	70	79	74	69	65	60	57	54	48	46	44	36	35	34	29	29	29
3	80	71	65	59	73	65	59	55	54	49	46	43	40	38	33	31	30	25	25	25
4	74	64	56	51	67	58	52	47	48	43	40	39	35	33	30	28	26	22	22	22
5	68	57	49	44	62	52	46	41	43	38	35	35	32	29	27	25	23	20	20	20
6	63	51	44	38	57	47	41	36	39	34	31	32	28	26	25	23	21	18	18	18
7	58	47	39	34	53	43	36	32	36	31	27	29	26	23	23	21	19	16	16	16
8	54	42	35	30	49	39	33	28	33	28	24	27	23	21	21	19	17	15	15	15
9	50	39	32	27	46	36	30	25	30	25	22	25	21	19	20	17	16	13	13	13
10	47	36	29	24	43	33	27	23	28	23	20	23	20	17	18	16	14	12	12	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	22478	22478	22478	22478
5°	22530	23875	22609	19073
10°	22282	25236	22441	15751
15°	21799	25244	22168	11832
20°	21217	20866	21680	9762
25°	20512	13039	20956	8305
30°	19613	8348	20146	7150
35°	18517	6415	19117	6118
40°	17296	5393	18035	5351
45°	15991	4591	16660	4492
50°	14654	3900	15338	3886
55°	13174	3390	13883	3345
60°	11859	2584	12487	2553
65°	10629	1944	11262	2206
70°	9272	1553	10000	1797
75°	7837	1191	8559	1361
80°	6227	809	6698	891
85°	4322	419	4746	440

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 20563 cd/sqm

TEST NUMBER: P1010122

CATALOG NUMBER: S122RDIP-B675D1080UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.7	2.1
10°-20°	376.0	5.8
20°-30°	483.9	7.4
30°-40°	459.0	7.1
40°-50°	393.4	6.1
50°-60°	299.6	4.6
60°-70°	188.9	2.9
70°-80°	94.3	1.5
80°-90°	28.0	0.4
90°-100°	226.3	3.5
100°-110°	796.9	12.3
110°-120°	836.9	12.9
120°-130°	688.5	10.6
130°-140°	553.1	8.5
140°-150°	417.8	6.4
150°-160°	293.7	4.5
160°-170°	172.9	2.7
170°-180°	56.2	0.9
0°-30°	994.5	15.3
0°-40°	1453.6	22.4
0°-60°	2146.6	33.0
0°-90°	2457.7	37.8
90°-120°	1860.0	28.6
90°-150°	3519.4	54.1
90°-180°	4042.0	62.2
0°-180°	6500.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1420	1420	1420	1420	1420	
5°	1421	1580	1426	1262	1421	135
15°	1339	1783	1362	836	1339	377
25°	1188	951	1214	606	1188	546
35°	975	469	1007	447	975	610
45°	732	326	763	319	732	565
55°	494	226	521	223	494	446
65°	299	117	317	133	299	297
75°	140	62	153	71	140	152
85°	31	18	34	19	31	35
90°	1	37	1	37	1	4
95°	39	127	39	127	39	40
105°	136	1258	136	1258	136	145
115°	240	1655	240	1655	240	238
125°	335	1343	335	1343	335	298
135°	393	1113	393	1113	393	304
145°	449	888	449	888	449	282
155°	510	747	510	747	510	235
165°	556	655	556	655	556	157
175°	579	590	579	590	579	55
180°	580	580	580	580	580	

TEST NUMBER: P1010122

CATALOG NUMBER: S122RDIP-B675D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1428.9	1434.8	1437.8	1441.7	1450.6	1456.5	1465.4	1467.4	1466.4	1470.4	1459.5
5°	1421.0	1433.9	1445.7	1455.6	1471.4	1481.2	1492.1	1504.9	1507.9	1522.7	1513.8
7.5°	1410.2	1428.9	1445.7	1465.4	1489.1	1501.9	1518.7	1538.5	1547.3	1565.1	1570.0
10°	1392.4	1419.1	1447.7	1468.4	1501.0	1523.7	1539.4	1571.0	1591.7	1618.4	1614.4
12.5°	1363.8	1398.3	1436.8	1471.4	1513.8	1528.6	1558.2	1590.8	1617.4	1642.1	1663.8
15°	1339.1	1378.6	1421.0	1463.5	1511.8	1539.4	1569.0	1611.5	1640.1	1683.5	1702.3
17.5°	1305.6	1355.9	1406.2	1453.6	1510.8	1542.4	1578.9	1620.4	1662.8	1704.2	1719.0
20°	1271.0	1325.3	1379.6	1443.7	1508.9	1539.4	1576.9	1628.3	1669.7	1702.3	1702.3
22.5°	1229.6	1295.7	1357.9	1419.1	1490.1	1534.5	1573.0	1633.2	1662.8	1669.7	1643.1
25°	1188.1	1254.3	1322.3	1398.3	1479.2	1518.7	1562.1	1618.4	1628.3	1600.6	1531.5
27.5°	1138.8	1212.8	1289.8	1371.7	1456.5	1505.9	1545.4	1582.9	1564.1	1490.1	1382.5
30°	1088.5	1168.4	1255.2	1333.2	1435.8	1481.2	1514.8	1525.6	1466.4	1346.0	1206.9
32.5°	1036.2	1114.1	1205.9	1299.6	1403.3	1446.7	1468.4	1439.8	1331.2	1179.3	1009.5
35°	975.0	1062.8	1158.5	1256.2	1358.9	1391.4	1404.2	1334.2	1195.0	998.7	829.9
37.5°	919.7	1007.5	1110.2	1209.8	1309.5	1327.3	1314.4	1204.9	1028.3	833.9	669.1
40°	854.6	948.3	1049.0	1160.5	1242.4	1247.3	1215.8	1073.7	854.6	672.0	570.4
42.5°	794.4	889.1	989.8	1103.3	1165.4	1148.7	1106.2	919.7	713.5	579.3	497.4
45°	732.2	822.0	930.6	1031.2	1075.6	1036.2	972.0	773.7	599.0	498.3	435.2
47.5°	672.0	755.9	863.5	960.2	968.1	923.7	847.7	648.3	519.1	438.1	386.8
50°	612.8	696.7	797.4	877.3	869.4	808.2	722.4	563.5	451.0	386.8	344.4
52.5°	553.6	629.6	727.3	790.4	756.9	697.7	612.8	477.6	393.7	337.5	304.9
55°	494.4	565.4	649.3	701.6	648.3	580.3	520.1	409.5	341.4	296.0	271.4
57.5°	445.1	501.3	578.3	609.9	545.7	492.4	440.1	352.3	296.0	263.5	234.9
60°	390.8	442.1	505.3	524.0	457.9	414.5	370.1	298.0	253.6	225.0	206.2
62.5°	344.4	386.8	435.2	435.2	377.0	344.4	310.8	249.7	213.2	190.5	181.6
65°	299.0	329.6	364.1	360.2	310.8	282.2	255.6	206.2	178.6	162.8	153.9
67.5°	254.6	278.3	301.0	287.2	251.6	227.0	202.3	166.8	148.0	137.2	125.3
70°	214.1	232.9	244.7	231.9	196.4	175.7	157.9	134.2	119.4	105.6	98.7
72.5°	179.6	187.5	191.4	175.7	146.0	134.2	121.4	104.6	91.8	84.9	82.9
75°	140.1	147.0	144.1	132.2	107.6	98.7	88.8	77.0	74.0	70.1	68.1
77.5°	109.5	109.5	104.6	93.7	77.0	70.1	66.1	60.2	57.2	56.2	54.3
80°	78.0	77.0	74.0	62.2	52.3	48.4	48.4	44.4	43.4	41.4	41.4
82.5°	51.3	51.3	47.4	37.5	34.5	33.6	32.6	30.6	30.6	29.6	29.6
85°	30.6	28.6	23.7	20.7	19.7	19.7	18.7	17.8	18.7	17.8	17.8
87.5°	13.8	10.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9
90°	1.1	4.5	8.9	11.2	13.4	15.0	16.7	22.3	30.1	36.8	38.0
92.5°	16.7	23.4	32.4	38.0	46.9	53.0	59.2	89.3	131.7	169.7	171.9
95°	39.1	43.5	54.7	64.7	82.6	96.0	109.4	160.7	257.9	387.3	437.6
97.5°	58.0	64.7	77.0	91.5	111.6	126.7	141.8	207.6	342.7	551.4	713.3
100°	86.0	89.3	99.3	117.2	139.5	155.2	170.8	229.9	366.1	607.2	881.8
102.5°	111.6	113.9	123.9	141.8	165.2	180.8	196.5	250.0	367.2	586.0	887.4
105°	136.2	140.6	148.5	165.2	189.8	205.4	221.0	273.5	372.8	557.0	827.1
107.5°	163.0	166.3	174.1	189.8	214.3	230.0	245.6	296.9	385.1	541.4	771.3
110°	189.8	194.2	200.9	215.4	238.9	255.0	271.2	320.4	400.7	536.9	733.4

TEST NUMBER: P1010122

CATALOG NUMBER: S122RDIP-B675D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	214.3	218.8	226.6	240.0	262.3	279.0	295.8	342.7	417.5	538.0	708.8
115°	240.0	245.6	252.3	265.7	288.0	303.0	318.1	366.1	434.2	542.5	692.1
117.5°	266.8	271.2	277.9	290.2	311.4	327.0	342.7	387.3	452.1	549.2	683.1
120°	291.3	295.8	302.5	312.6	334.9	350.5	366.1	409.7	469.9	555.9	675.3
122.5°	314.8	318.1	324.8	336.0	358.3	374.5	390.7	430.9	485.6	563.7	670.9
125°	334.9	338.2	344.9	358.3	380.6	396.2	411.9	452.1	502.3	571.5	665.3
127.5°	351.6	356.1	365.0	379.5	400.7	416.9	433.1	472.2	517.9	579.3	661.9
130°	366.1	370.6	381.8	397.4	419.7	435.4	451.0	490.0	532.5	588.3	659.7
132.5°	379.5	385.1	397.4	414.1	437.6	453.2	468.8	505.7	547.0	597.2	658.6
135°	392.9	397.4	410.8	427.5	453.2	468.8	484.5	520.2	559.2	603.9	657.5
137.5°	405.2	410.8	424.2	442.0	467.7	482.2	496.7	532.5	569.3	610.6	657.5
140°	419.7	424.2	437.6	455.4	480.0	494.5	509.0	542.5	577.1	615.1	656.4
142.5°	434.2	437.6	449.8	467.7	491.2	504.6	517.9	550.3	583.8	618.4	656.4
145°	448.7	453.2	464.4	481.1	503.4	515.7	528.0	558.1	589.4	620.6	654.1
147.5°	464.4	467.7	478.9	494.5	513.5	524.6	535.8	564.8	592.7	621.8	650.8
150°	480.0	483.3	492.3	506.8	523.5	533.6	543.6	569.3	595.0	620.6	647.4
152.5°	495.6	496.7	505.7	517.9	533.6	542.5	551.4	573.8	596.1	618.4	641.8
155°	510.1	511.2	517.9	530.2	542.5	550.8	559.2	578.2	597.2	616.2	635.1
157.5°	522.4	523.5	529.1	540.3	550.3	557.6	564.8	581.6	597.2	611.7	628.4
160°	534.7	535.8	540.3	549.2	558.1	564.2	570.4	583.8	597.2	608.4	621.8
162.5°	547.0	545.8	550.3	557.0	564.8	569.3	573.8	584.9	596.1	605.0	616.2
165°	555.9	554.8	557.0	563.7	569.3	572.6	576.0	586.0	593.8	600.5	608.4
167.5°	563.7	562.6	564.8	569.3	573.8	576.0	578.2	586.0	592.7	596.1	601.7
170°	571.5	569.3	570.4	573.8	576.0	577.6	579.3	584.9	590.5	592.7	596.1
172.5°	576.0	574.9	573.8	577.1	578.2	579.4	580.5	583.8	587.1	588.3	589.4
175°	579.3	578.2	577.1	579.3	579.3	579.9	580.5	582.7	584.9	583.8	584.9
177.5°	581.6	579.3	578.2	580.5	580.5	580.5	580.5	581.6	583.8	581.6	580.5
180°	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5

TEST NUMBER: P1010122

CATALOG NUMBER: S122RDIP-B675D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1470.4	1472.3	1475.3	1489.1	1491.1	1495.0	1493.1	1493.1	1494.0	1492.1	1493.1
5°	1533.5	1536.5	1551.3	1568.1	1572.0	1568.1	1573.0	1579.9	1579.9	1579.9	1577.9
7.5°	1592.7	1603.6	1620.4	1645.0	1650.0	1654.9	1663.8	1657.9	1659.8	1668.7	1665.8
10°	1650.0	1665.8	1684.5	1705.2	1716.1	1723.0	1726.9	1735.8	1756.5	1732.9	1741.7
12.5°	1704.2	1726.9	1746.7	1769.4	1777.3	1786.1	1789.1	1797.0	1797.0	1796.0	1802.9
15°	1739.8	1760.5	1778.3	1793.1	1795.0	1793.1	1791.1	1792.1	1795.0	1783.2	1790.1
17.5°	1747.7	1749.6	1755.6	1749.6	1750.6	1729.9	1718.1	1715.1	1687.5	1688.5	1711.1
20°	1709.2	1675.6	1666.7	1634.2	1614.4	1561.2	1559.2	1544.4	1486.2	1503.9	1500.0
22.5°	1603.6	1546.4	1470.4	1432.9	1414.1	1357.9	1314.4	1283.9	1263.1	1242.4	1233.5
25°	1464.4	1371.7	1264.1	1190.1	1179.3	1127.0	1047.0	1009.5	965.1	951.3	975.0
27.5°	1284.8	1164.4	1043.1	929.6	908.9	861.5	821.0	794.4	743.1	740.1	742.1
30°	1041.1	919.7	818.1	744.1	692.7	671.0	644.4	624.7	603.9	611.8	613.8
32.5°	855.6	740.1	645.4	605.9	582.2	568.4	545.7	532.9	524.0	521.0	520.1
35°	679.9	602.9	560.5	522.0	508.2	498.3	481.6	475.6	467.8	468.7	468.7
37.5°	582.2	518.1	486.5	466.8	453.9	449.0	438.1	432.2	427.3	425.3	428.3
40°	502.3	457.9	438.1	420.4	409.5	407.6	401.6	394.7	388.8	389.8	392.8
42.5°	444.1	418.4	394.7	380.9	373.0	370.1	365.1	360.2	360.2	357.2	356.2
45°	397.7	377.0	357.2	344.4	339.5	335.5	329.6	328.6	324.7	325.7	326.6
47.5°	356.2	339.5	324.7	311.8	306.9	305.9	300.0	296.0	296.0	295.1	294.1
50°	318.7	302.0	289.1	282.2	275.3	273.3	272.4	271.4	269.4	269.4	270.4
52.5°	288.2	271.4	261.5	255.6	251.6	249.7	249.7	248.7	248.7	248.7	247.7
55°	254.6	240.8	232.9	230.9	228.9	228.0	227.0	225.0	224.0	226.0	224.0
57.5°	223.0	218.1	211.2	209.2	204.3	204.3	201.3	199.3	197.4	199.3	199.3
60°	198.4	191.4	187.5	181.6	177.6	173.7	168.7	167.8	165.8	164.8	163.8
62.5°	172.7	166.8	156.9	148.0	142.1	138.2	136.2	135.2	135.2	134.2	134.2
65°	144.1	130.3	125.3	122.4	121.4	120.4	118.4	117.4	118.4	117.4	118.4
67.5°	112.5	110.5	107.6	105.6	104.6	103.6	103.6	102.6	102.6	102.6	102.6
70°	97.7	92.8	91.8	89.8	89.8	88.8	88.8	88.8	88.8	87.8	89.8
72.5°	80.9	78.0	77.0	76.0	76.0	76.0	75.0	75.0	75.0	74.0	75.0
75°	66.1	65.1	63.2	63.2	62.2	63.2	62.2	62.2	61.2	62.2	62.2
77.5°	53.3	52.3	51.3	51.3	50.3	50.3	50.3	50.3	50.3	50.3	51.3
80°	40.5	39.5	38.5	39.5	38.5	39.5	38.5	38.5	39.5	38.5	38.5
82.5°	29.6	28.6	28.6	27.6	27.6	27.6	27.6	27.6	27.6	27.6	27.6
85°	17.8	16.8	16.8	17.8	16.8	17.8	16.8	16.8	16.8	17.8	17.8
87.5°	7.9	8.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	8.9
90°	36.8	35.7	33.5	35.7	36.2	36.8	36.8	36.8	36.8	36.8	36.8
92.5°	144.0	112.7	96.0	83.7	79.2	74.8	73.7	69.2	70.3	68.1	70.3
95°	382.9	292.5	224.4	177.5	165.2	152.9	138.4	129.5	126.1	127.3	126.1
97.5°	718.9	598.3	477.8	365.0	331.5	298.0	254.5	232.2	219.9	213.2	219.9
100°	1042.6	1019.1	880.7	727.8	660.2	592.7	500.1	452.1	419.7	399.6	419.7
102.5°	1163.1	1294.9	1290.4	1188.8	1116.2	1043.7	941.0	850.6	808.2	779.1	808.2
105°	1124.1	1356.2	1482.4	1496.9	1478.5	1460.1	1390.8	1321.6	1273.6	1258.0	1273.6
107.5°	1041.5	1290.4	1477.9	1587.3	1609.6	1632.0	1630.8	1620.8	1606.3	1580.6	1606.3
110°	964.4	1200.0	1399.8	1542.7	1588.4	1634.2	1682.2	1703.4	1713.4	1712.3	1713.4

TEST NUMBER: P1010122

CATALOG NUMBER: S122RDIP-B675D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	910.9	1117.4	1307.1	1462.3	1516.4	1570.6	1642.0	1681.1	1702.3	1710.1	1702.3
115°	868.4	1052.6	1224.5	1370.8	1428.2	1485.7	1565.0	1616.3	1645.4	1655.4	1645.4
117.5°	839.4	999.0	1153.1	1289.3	1344.0	1398.7	1480.1	1534.8	1565.0	1572.8	1565.0
120°	817.1	961.1	1099.5	1217.8	1268.6	1319.4	1397.5	1450.0	1482.4	1493.5	1482.4
122.5°	798.1	931.0	1054.9	1165.4	1210.1	1254.7	1322.8	1374.1	1402.0	1410.9	1402.0
125°	780.3	901.9	1016.9	1115.1	1157.0	1198.9	1263.6	1306.0	1333.9	1342.8	1333.9
127.5°	763.5	872.9	979.0	1072.7	1111.8	1150.9	1207.8	1248.0	1272.5	1279.2	1272.5
130°	746.8	845.0	941.0	1029.2	1066.1	1102.9	1157.6	1195.5	1217.8	1226.8	1217.8
132.5°	733.4	818.2	905.3	984.5	1018.6	1052.6	1106.2	1144.2	1164.2	1172.1	1164.2
135°	721.1	793.7	867.3	941.0	972.2	1003.5	1051.5	1088.3	1108.4	1112.9	1108.4
137.5°	712.2	773.6	837.2	897.5	925.4	953.3	999.0	1031.4	1049.3	1056.0	1049.3
140°	704.4	754.6	808.2	859.5	884.0	908.6	944.3	973.4	990.1	996.8	990.1
142.5°	696.5	739.0	782.5	824.9	844.4	864.0	897.5	923.1	937.7	937.7	937.7
145°	689.8	724.4	761.3	795.9	812.1	828.3	855.0	874.0	885.2	888.5	885.2
147.5°	683.1	713.3	743.4	771.3	783.6	795.9	819.3	835.0	842.8	845.0	842.8
150°	674.2	701.0	725.6	749.0	759.0	769.1	785.8	799.2	805.9	807.0	805.9
152.5°	666.4	688.7	711.1	730.0	738.4	746.8	759.1	770.2	774.7	774.7	774.7
155°	656.4	677.6	695.4	712.2	718.3	724.4	736.7	744.5	749.0	746.8	749.0
157.5°	647.4	664.2	679.8	694.3	699.3	704.4	713.3	720.0	722.2	722.2	722.2
160°	637.4	651.9	664.2	676.4	680.3	684.3	692.1	697.7	698.8	698.8	698.8
162.5°	628.4	639.6	649.7	659.7	662.5	665.3	673.1	676.4	677.6	676.4	677.6
165°	618.4	627.3	635.1	643.0	645.2	647.4	651.9	656.4	656.4	655.2	656.4
167.5°	608.4	615.1	621.8	627.3	629.6	631.8	634.0	636.3	636.3	635.1	636.3
170°	600.5	606.1	609.5	613.9	615.0	616.2	617.3	620.6	619.5	617.3	619.5
172.5°	592.7	596.1	598.3	601.7	602.2	602.8	603.9	605.0	603.9	602.8	603.9
175°	586.0	589.4	590.5	591.6	592.2	592.7	592.7	593.8	592.7	590.5	592.7
177.5°	581.6	583.8	583.8	584.9	584.9	584.9	584.9	584.9	583.8	581.6	583.8
180°	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5

TEST NUMBER: P1010122

CATALOG NUMBER: S122RDIP-B675D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1497.0	1490.1	1488.1	1490.1	1488.1	1489.1	1482.2	1456.5	1463.5	1452.6	1458.5
5°	1581.9	1576.0	1563.1	1561.2	1559.2	1557.2	1547.3	1524.6	1515.8	1501.0	1500.0
7.5°	1662.8	1662.8	1652.9	1646.0	1637.1	1630.2	1617.4	1583.8	1570.0	1552.3	1542.4
10°	1742.7	1717.1	1727.9	1721.0	1699.3	1695.4	1671.7	1651.9	1625.3	1607.5	1591.7
12.5°	1800.0	1792.1	1782.2	1776.3	1770.4	1757.5	1741.7	1691.4	1677.6	1642.1	1624.3
15°	1798.0	1793.1	1796.0	1796.0	1794.0	1791.1	1778.3	1741.7	1718.1	1683.5	1652.9
17.5°	1701.3	1714.1	1726.9	1735.8	1755.6	1764.4	1776.3	1754.6	1739.8	1710.2	1677.6
20°	1532.5	1564.1	1601.6	1609.5	1627.3	1679.6	1703.3	1722.0	1727.9	1718.1	1691.4
22.5°	1297.7	1324.3	1415.1	1413.1	1438.8	1501.0	1570.0	1626.3	1670.7	1695.4	1685.5
25°	1016.4	1053.9	1102.3	1138.8	1222.7	1315.4	1401.3	1491.1	1568.1	1636.2	1652.9
27.5°	768.7	818.1	856.6	904.9	947.3	1056.9	1167.4	1307.5	1397.3	1526.6	1593.7
30°	621.7	644.4	682.9	705.6	726.3	810.2	935.5	1073.7	1231.6	1380.6	1496.0
32.5°	530.9	546.7	575.3	585.2	606.9	663.1	742.1	868.4	1031.2	1211.8	1363.8
35°	476.6	493.4	499.3	508.2	526.0	561.5	615.8	707.6	854.6	1031.2	1212.8
37.5°	430.3	439.1	455.9	461.8	467.8	494.4	530.9	595.1	692.7	837.8	1039.1
40°	397.7	402.6	411.5	416.4	420.4	439.1	471.7	515.1	587.2	697.7	883.2
42.5°	363.2	369.1	375.0	380.9	385.8	400.6	420.4	461.8	510.2	594.1	728.3
45°	329.6	333.5	340.5	344.4	351.3	363.2	380.9	409.5	453.0	506.2	614.8
47.5°	299.0	303.9	306.9	311.8	316.8	329.6	346.4	365.1	400.6	453.0	531.9
50°	271.4	277.3	281.2	282.2	286.2	298.0	311.8	332.6	355.3	395.7	464.8
52.5°	251.6	252.6	255.6	259.5	258.5	265.5	278.3	294.1	317.8	350.3	400.6
55°	228.9	231.9	233.9	234.9	234.9	240.8	247.7	262.5	281.2	307.9	350.3
57.5°	200.3	203.3	209.2	211.2	214.1	217.1	220.1	229.9	245.7	271.4	305.9
60°	170.7	172.7	178.6	182.6	184.5	192.4	196.4	204.3	213.2	231.9	264.5
62.5°	137.2	139.1	142.1	146.0	150.0	161.8	171.7	179.6	186.5	199.3	226.0
65°	119.4	120.4	122.4	123.4	124.3	129.3	138.2	149.0	161.8	171.7	187.5
67.5°	103.6	104.6	105.6	107.6	108.6	109.5	113.5	116.4	129.3	143.1	154.9
70°	88.8	90.8	91.8	91.8	92.8	94.7	96.7	100.7	104.6	111.5	126.3
72.5°	75.0	76.0	78.0	78.0	78.0	79.9	81.9	83.9	85.9	89.8	95.7
75°	62.2	64.1	64.1	64.1	65.1	65.1	67.1	69.1	71.1	74.0	76.0
77.5°	51.3	51.3	51.3	51.3	52.3	52.3	53.3	55.3	56.2	57.2	59.2
80°	38.5	39.5	39.5	39.5	40.5	40.5	40.5	42.4	43.4	43.4	45.4
82.5°	28.6	28.6	28.6	29.6	28.6	29.6	29.6	30.6	29.6	30.6	31.6
85°	17.8	17.8	17.8	18.7	18.7	18.7	18.7	18.7	18.7	18.7	19.7
87.5°	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9	9.9	8.9	8.9
90°	36.8	36.8	36.8	36.2	35.7	33.5	35.7	36.8	38.0	36.8	30.1
92.5°	69.2	73.7	74.8	79.2	83.7	96.0	112.7	144.0	171.9	169.7	131.7
95°	129.5	138.4	152.9	165.2	177.5	224.4	292.5	382.9	437.6	387.3	257.9
97.5°	232.2	254.5	298.0	331.5	365.0	477.8	598.3	718.9	713.3	551.4	342.7
100°	452.1	500.1	592.7	660.2	727.8	880.7	1019.1	1042.6	881.8	607.2	366.1
102.5°	850.6	941.0	1043.7	1116.2	1188.8	1290.4	1294.9	1163.1	887.4	586.0	367.2
105°	1321.6	1390.8	1460.1	1478.5	1496.9	1482.4	1356.2	1124.1	827.1	557.0	372.8
107.5°	1620.8	1630.8	1632.0	1609.6	1587.3	1477.9	1290.4	1041.5	771.3	541.4	385.1
110°	1703.4	1682.2	1634.2	1588.4	1542.7	1399.8	1200.0	964.4	733.4	536.9	400.7

TEST NUMBER: P1010122

CATALOG NUMBER: S122RDIP-B675D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1681.1	1642.0	1570.6	1516.4	1462.3	1307.1	1117.4	910.9	708.8	538.0	417.5
115°	1616.3	1565.0	1485.7	1428.2	1370.8	1224.5	1052.6	868.4	692.1	542.5	434.2
117.5°	1534.8	1480.1	1398.7	1344.0	1289.3	1153.1	999.0	839.4	683.1	549.2	452.1
120°	1450.0	1397.5	1319.4	1268.6	1217.8	1099.5	961.1	817.1	675.3	555.9	469.9
122.5°	1374.1	1322.8	1254.7	1210.1	1165.4	1054.9	931.0	798.1	670.9	563.7	485.6
125°	1306.0	1263.6	1198.9	1157.0	1115.1	1016.9	901.9	780.3	665.3	571.5	502.3
127.5°	1248.0	1207.8	1150.9	1111.8	1072.7	979.0	872.9	763.5	661.9	579.3	517.9
130°	1195.5	1157.6	1102.9	1066.1	1029.2	941.0	845.0	746.8	659.7	588.3	532.5
132.5°	1144.2	1106.2	1052.6	1018.6	984.5	905.3	818.2	733.4	658.6	597.2	547.0
135°	1088.3	1051.5	1003.5	972.2	941.0	867.3	793.7	721.1	657.5	603.9	559.2
137.5°	1031.4	999.0	953.3	925.4	897.5	837.2	773.6	712.2	657.5	610.6	569.3
140°	973.4	944.3	908.6	884.0	859.5	808.2	754.6	704.4	656.4	615.1	577.1
142.5°	923.1	897.5	864.0	844.4	824.9	782.5	739.0	696.5	656.4	618.4	583.8
145°	874.0	855.0	828.3	812.1	795.9	761.3	724.4	689.8	654.1	620.6	589.4
147.5°	835.0	819.3	795.9	783.6	771.3	743.4	713.3	683.1	650.8	621.8	592.7
150°	799.2	785.8	769.1	759.0	749.0	725.6	701.0	674.2	647.4	620.6	595.0
152.5°	770.2	759.1	746.8	738.4	730.0	711.1	688.7	666.4	641.8	618.4	596.1
155°	744.5	736.7	724.4	718.3	712.2	695.4	677.6	656.4	635.1	616.2	597.2
157.5°	720.0	713.3	704.4	699.3	694.3	679.8	664.2	647.4	628.4	611.7	597.2
160°	697.7	692.1	684.3	680.3	676.4	664.2	651.9	637.4	621.8	608.4	597.2
162.5°	676.4	673.1	665.3	662.5	659.7	649.7	639.6	628.4	616.2	605.0	596.1
165°	656.4	651.9	647.4	645.2	643.0	635.1	627.3	618.4	608.4	600.5	593.8
167.5°	636.3	634.0	631.8	629.6	627.3	621.8	615.1	608.4	601.7	596.1	592.7
170°	620.6	617.3	616.2	615.0	613.9	609.5	606.1	600.5	596.1	592.7	590.5
172.5°	605.0	603.9	602.8	602.2	601.7	598.3	596.1	592.7	589.4	588.3	587.1
175°	593.8	592.7	592.7	592.2	591.6	590.5	589.4	586.0	584.9	583.8	584.9
177.5°	584.9	584.9	584.9	584.9	584.9	583.8	583.8	581.6	580.5	581.6	583.8
180°	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5

TEST NUMBER: P1010122

CATALOG NUMBER: S122RDIP-B675D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1449.6	1444.7	1444.7	1441.7	1441.7	1426.0	1426.0	1430.9	1425.0	1418.1	1408.2
5°	1487.1	1476.3	1473.3	1469.4	1456.5	1436.8	1428.9	1426.0	1414.1	1399.3	1382.5
7.5°	1522.7	1504.9	1496.0	1487.1	1470.4	1442.7	1426.9	1416.1	1398.3	1375.6	1353.9
10°	1557.2	1534.5	1511.8	1501.0	1477.3	1442.7	1420.0	1402.3	1376.6	1346.0	1315.4
12.5°	1588.8	1541.4	1537.5	1515.8	1481.2	1441.7	1407.2	1381.6	1349.0	1313.5	1277.9
15°	1616.4	1568.1	1544.4	1524.6	1479.2	1429.9	1393.4	1361.8	1318.4	1277.9	1234.5
17.5°	1630.2	1577.9	1562.1	1529.6	1483.2	1419.1	1369.7	1331.2	1283.9	1235.5	1186.2
20°	1644.0	1582.9	1557.2	1534.5	1471.4	1398.3	1343.1	1298.7	1246.4	1189.1	1134.8
22.5°	1651.0	1582.9	1552.3	1520.7	1459.5	1375.6	1310.5	1258.2	1197.0	1138.8	1073.7
25°	1639.1	1576.9	1540.4	1507.9	1438.8	1348.0	1273.0	1213.8	1148.7	1082.5	1016.4
27.5°	1609.5	1563.1	1520.7	1487.1	1410.2	1312.5	1233.5	1166.4	1099.3	1025.3	958.2
30°	1554.2	1533.5	1500.0	1462.5	1378.6	1280.9	1187.1	1118.1	1044.1	970.0	900.0
32.5°	1468.4	1486.2	1464.4	1431.9	1341.1	1237.5	1137.8	1067.7	986.8	906.9	842.7
35°	1363.8	1426.9	1415.1	1392.4	1301.6	1191.1	1091.4	1006.6	925.6	844.7	780.6
37.5°	1249.3	1345.0	1354.9	1341.1	1256.2	1143.7	1034.2	951.3	868.4	786.5	721.4
40°	1092.4	1239.4	1271.0	1276.9	1208.9	1086.5	972.0	891.1	809.2	729.3	650.3
42.5°	948.3	1133.9	1173.3	1198.0	1148.7	1030.2	914.8	825.0	744.1	672.0	593.1
45°	813.1	1006.6	1070.7	1102.3	1080.6	966.1	846.7	762.8	688.8	622.7	546.7
47.5°	674.0	868.4	958.2	1008.5	1008.5	901.0	781.6	698.7	627.6	571.4	504.3
50°	581.2	743.1	835.8	902.0	919.7	834.9	722.4	641.4	574.3	513.1	461.8
52.5°	495.4	640.4	717.4	786.5	837.8	763.8	656.2	583.2	517.1	459.9	419.4
55°	428.3	536.8	606.9	682.9	740.1	691.8	592.1	521.0	463.8	416.4	381.9
57.5°	364.1	458.9	516.1	583.2	644.4	607.9	527.9	466.8	416.4	375.0	344.4
60°	309.9	386.8	431.2	483.5	559.5	533.9	467.8	411.5	371.0	333.5	307.9
62.5°	263.5	324.7	362.2	399.7	468.7	456.9	405.6	362.2	327.6	296.0	274.3
65°	216.1	266.4	296.0	328.6	383.9	388.8	347.4	316.8	285.2	257.6	237.8
67.5°	174.7	214.1	240.8	268.4	312.8	326.6	298.0	272.4	245.7	223.0	205.3
70°	141.1	168.7	188.5	210.2	246.7	263.5	248.7	230.9	209.2	190.5	174.7
72.5°	111.5	129.3	141.1	157.9	187.5	204.3	203.3	187.5	171.7	158.9	146.0
75°	81.9	95.7	105.6	116.4	140.1	155.9	159.9	153.0	137.2	127.3	117.4
77.5°	62.2	70.1	75.0	82.9	99.7	113.5	119.4	117.4	106.6	98.7	91.8
80°	47.4	49.3	51.3	54.3	68.1	80.9	84.9	83.9	78.0	75.0	67.1
82.5°	33.6	34.5	35.5	36.5	41.4	52.3	56.2	58.2	53.3	50.3	43.4
85°	19.7	20.7	20.7	22.7	23.7	26.6	33.6	33.6	32.6	28.6	27.6
87.5°	9.9	9.9	8.9	8.9	9.9	10.9	12.8	14.8	12.8	11.8	10.9
90°	22.3	16.7	15.0	13.4	11.2	8.9	4.5	1.1	4.5	8.9	11.2
92.5°	89.3	59.2	53.0	46.9	38.0	32.4	23.4	16.7	23.4	32.4	38.0
95°	160.7	109.4	96.0	82.6	64.7	54.7	43.5	39.1	43.5	54.7	64.7
97.5°	207.6	141.8	126.7	111.6	91.5	77.0	64.7	58.0	64.7	77.0	91.5
100°	229.9	170.8	155.2	139.5	117.2	99.3	89.3	86.0	89.3	99.3	117.2
102.5°	250.0	196.5	180.8	165.2	141.8	123.9	113.9	111.6	113.9	123.9	141.8
105°	273.5	221.0	205.4	189.8	165.2	148.5	140.6	136.2	140.6	148.5	165.2
107.5°	296.9	245.6	230.0	214.3	189.8	174.1	166.3	163.0	166.3	174.1	189.8
110°	320.4	271.2	255.0	238.9	215.4	200.9	194.2	189.8	194.2	200.9	215.4

TEST NUMBER: P1010122

CATALOG NUMBER: S122RDIP-B675D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	342.7	295.8	279.0	262.3	240.0	226.6	218.8	214.3	218.8	226.6	240.0
115°	366.1	318.1	303.0	288.0	265.7	252.3	245.6	240.0	245.6	252.3	265.7
117.5°	387.3	342.7	327.0	311.4	290.2	277.9	271.2	266.8	271.2	277.9	290.2
120°	409.7	366.1	350.5	334.9	312.6	302.5	295.8	291.3	295.8	302.5	312.6
122.5°	430.9	390.7	374.5	358.3	336.0	324.8	318.1	314.8	318.1	324.8	336.0
125°	452.1	411.9	396.2	380.6	358.3	344.9	338.2	334.9	338.2	344.9	358.3
127.5°	472.2	433.1	416.9	400.7	379.5	365.0	356.1	351.6	356.1	365.0	379.5
130°	490.0	451.0	435.4	419.7	397.4	381.8	370.6	366.1	370.6	381.8	397.4
132.5°	505.7	468.8	453.2	437.6	414.1	397.4	385.1	379.5	385.1	397.4	414.1
135°	520.2	484.5	468.8	453.2	427.5	410.8	397.4	392.9	397.4	410.8	427.5
137.5°	532.5	496.7	482.2	467.7	442.0	424.2	410.8	405.2	410.8	424.2	442.0
140°	542.5	509.0	494.5	480.0	455.4	437.6	424.2	419.7	424.2	437.6	455.4
142.5°	550.3	517.9	504.6	491.2	467.7	449.8	437.6	434.2	437.6	449.8	467.7
145°	558.1	528.0	515.7	503.4	481.1	464.4	453.2	448.7	453.2	464.4	481.1
147.5°	564.8	535.8	524.6	513.5	494.5	478.9	467.7	464.4	467.7	478.9	494.5
150°	569.3	543.6	533.6	523.5	506.8	492.3	483.3	480.0	483.3	492.3	506.8
152.5°	573.8	551.4	542.5	533.6	517.9	505.7	496.7	495.6	496.7	505.7	517.9
155°	578.2	559.2	550.8	542.5	530.2	517.9	511.2	510.1	511.2	517.9	530.2
157.5°	581.6	564.8	557.6	550.3	540.3	529.1	523.5	522.4	523.5	529.1	540.3
160°	583.8	570.4	564.2	558.1	549.2	540.3	535.8	534.7	535.8	540.3	549.2
162.5°	584.9	573.8	569.3	564.8	557.0	550.3	545.8	547.0	545.8	550.3	557.0
165°	586.0	576.0	572.6	569.3	563.7	557.0	554.8	555.9	554.8	557.0	563.7
167.5°	586.0	578.2	576.0	573.8	569.3	564.8	562.6	563.7	562.6	564.8	569.3
170°	584.9	579.3	577.6	576.0	573.8	570.4	569.3	571.5	569.3	570.4	573.8
172.5°	583.8	580.5	579.4	578.2	577.1	573.8	574.9	576.0	574.9	573.8	577.1
175°	582.7	580.5	579.9	579.3	579.3	577.1	578.2	579.3	578.2	577.1	579.3
177.5°	581.6	580.5	580.5	580.5	580.5	578.2	579.3	581.6	579.3	578.2	580.5
180°	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5

TEST NUMBER: P1010122

CATALOG NUMBER: S122RDIP-B675D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1404.2	1405.2	1408.2	1399.3	1385.5	1379.6	1361.8	1358.9	1355.9	1355.9	1358.9
5°	1372.7	1368.7	1369.7	1352.9	1333.2	1321.4	1296.7	1300.6	1287.8	1279.9	1281.9
7.5°	1338.1	1327.3	1326.3	1304.6	1279.9	1258.2	1232.5	1226.6	1214.8	1201.0	1195.0
10°	1294.7	1286.8	1272.0	1247.3	1215.8	1198.0	1163.5	1142.7	1139.8	1119.1	1111.2
12.5°	1250.3	1236.5	1221.7	1187.1	1151.6	1123.0	1097.3	1074.6	1058.9	1041.1	1029.3
15°	1199.0	1182.2	1165.4	1128.9	1087.5	1058.9	1020.4	986.8	940.4	903.9	883.2
17.5°	1142.7	1124.0	1101.3	1060.8	1020.4	980.9	909.8	870.4	837.8	816.1	803.3
20°	1084.5	1063.8	1041.1	1000.6	930.6	861.5	822.0	791.4	771.7	750.0	734.2
22.5°	1023.3	1001.6	977.0	913.8	839.8	791.4	760.8	732.2	703.6	691.8	683.9
25°	966.1	946.4	914.8	828.9	770.7	726.3	691.8	673.0	658.2	642.4	627.6
27.5°	906.9	870.4	826.0	753.9	717.4	672.0	647.4	633.5	607.9	597.0	590.1
30°	835.8	795.4	752.9	701.6	659.2	627.6	604.9	582.2	567.4	556.6	544.7
32.5°	763.8	725.3	698.7	645.4	613.8	581.2	559.5	545.7	524.0	517.1	512.2
35°	701.6	669.1	645.4	602.0	572.4	542.8	527.0	506.2	492.4	479.6	471.7
37.5°	640.4	622.7	598.0	561.5	529.9	506.2	484.5	477.6	458.9	452.0	444.1
40°	598.0	571.4	550.6	519.1	492.4	466.8	453.0	437.2	424.3	413.5	410.5
42.5°	546.7	527.0	515.1	480.6	453.0	438.1	421.4	403.6	393.7	384.9	374.0
45°	508.2	490.5	473.7	446.0	421.4	402.6	387.8	376.0	359.2	355.3	338.5
47.5°	467.8	450.0	437.2	409.5	386.8	369.1	358.2	342.4	328.6	319.7	311.8
50°	427.3	412.5	400.6	377.0	357.2	338.5	323.7	307.9	302.0	287.2	282.2
52.5°	388.8	378.9	366.1	343.4	323.7	307.9	292.1	279.3	270.4	262.5	256.6
55°	356.2	340.5	334.5	309.9	293.1	276.3	262.5	254.6	243.7	238.8	233.9
57.5°	319.7	310.8	301.0	282.2	263.5	247.7	237.8	226.0	220.1	214.1	210.2
60°	288.2	275.3	267.4	251.6	234.9	220.1	211.2	202.3	194.4	189.5	181.6
62.5°	251.6	241.8	236.8	220.1	206.2	192.4	184.5	175.7	169.7	160.9	151.0
65°	220.1	212.2	206.2	192.4	179.6	166.8	158.9	148.0	140.1	135.2	134.2
67.5°	192.4	186.5	177.6	164.8	152.0	142.1	133.2	124.3	123.4	121.4	121.4
70°	161.8	155.9	151.0	137.2	126.3	115.5	113.5	110.5	107.6	106.6	104.6
72.5°	135.2	130.3	124.3	112.5	101.6	98.7	96.7	94.7	91.8	90.8	89.8
75°	109.5	102.6	98.7	87.8	84.9	82.9	80.9	78.0	76.0	75.0	73.0
77.5°	83.9	77.0	77.0	71.1	69.1	66.1	64.1	62.2	61.2	59.2	59.2
80°	59.2	59.2	57.2	54.3	51.3	50.3	47.4	46.4	45.4	46.4	44.4
82.5°	43.4	39.5	39.5	37.5	35.5	34.5	32.6	32.6	31.6	31.6	31.6
85°	24.7	24.7	23.7	21.7	20.7	20.7	19.7	19.7	18.7	18.7	17.8
87.5°	9.9	8.9	9.9	8.9	8.9	7.9	7.9	7.9	6.9	7.9	6.9
90°	13.4	15.0	16.7	22.3	30.1	36.8	38.0	36.8	35.7	33.5	35.7
92.5°	46.9	53.0	59.2	89.3	131.7	169.7	171.9	144.0	112.7	96.0	83.7
95°	82.6	96.0	109.4	160.7	257.9	387.3	437.6	382.9	292.5	224.4	177.5
97.5°	111.6	126.7	141.8	207.6	342.7	551.4	713.3	718.9	598.3	477.8	365.0
100°	139.5	155.2	170.8	229.9	366.1	607.2	881.8	1042.6	1019.1	880.7	727.8
102.5°	165.2	180.8	196.5	250.0	367.2	586.0	887.4	1163.1	1294.9	1290.4	1188.8
105°	189.8	205.4	221.0	273.5	372.8	557.0	827.1	1124.1	1356.2	1482.4	1496.9
107.5°	214.3	230.0	245.6	296.9	385.1	541.4	771.3	1041.5	1290.4	1477.9	1587.3
110°	238.9	255.0	271.2	320.4	400.7	536.9	733.4	964.4	1200.0	1399.8	1542.7

TEST NUMBER: P1010122

CATALOG NUMBER: S122RDIP-B675D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	262.3	279.0	295.8	342.7	417.5	538.0	708.8	910.9	1117.4	1307.1	1462.3
115°	288.0	303.0	318.1	366.1	434.2	542.5	692.1	868.4	1052.6	1224.5	1370.8
117.5°	311.4	327.0	342.7	387.3	452.1	549.2	683.1	839.4	999.0	1153.1	1289.3
120°	334.9	350.5	366.1	409.7	469.9	555.9	675.3	817.1	961.1	1099.5	1217.8
122.5°	358.3	374.5	390.7	430.9	485.6	563.7	670.9	798.1	931.0	1054.9	1165.4
125°	380.6	396.2	411.9	452.1	502.3	571.5	665.3	780.3	901.9	1016.9	1115.1
127.5°	400.7	416.9	433.1	472.2	517.9	579.3	661.9	763.5	872.9	979.0	1072.7
130°	419.7	435.4	451.0	490.0	532.5	588.3	659.7	746.8	845.0	941.0	1029.2
132.5°	437.6	453.2	468.8	505.7	547.0	597.2	658.6	733.4	818.2	905.3	984.5
135°	453.2	468.8	484.5	520.2	559.2	603.9	657.5	721.1	793.7	867.3	941.0
137.5°	467.7	482.2	496.7	532.5	569.3	610.6	657.5	712.2	773.6	837.2	897.5
140°	480.0	494.5	509.0	542.5	577.1	615.1	656.4	704.4	754.6	808.2	859.5
142.5°	491.2	504.6	517.9	550.3	583.8	618.4	656.4	696.5	739.0	782.5	824.9
145°	503.4	515.7	528.0	558.1	589.4	620.6	654.1	689.8	724.4	761.3	795.9
147.5°	513.5	524.6	535.8	564.8	592.7	621.8	650.8	683.1	713.3	743.4	771.3
150°	523.5	533.6	543.6	569.3	595.0	620.6	647.4	674.2	701.0	725.6	749.0
152.5°	533.6	542.5	551.4	573.8	596.1	618.4	641.8	666.4	688.7	711.1	730.0
155°	542.5	550.8	559.2	578.2	597.2	616.2	635.1	656.4	677.6	695.4	712.2
157.5°	550.3	557.6	564.8	581.6	597.2	611.7	628.4	647.4	664.2	679.8	694.3
160°	558.1	564.2	570.4	583.8	597.2	608.4	621.8	637.4	651.9	664.2	676.4
162.5°	564.8	569.3	573.8	584.9	596.1	605.0	616.2	628.4	639.6	649.7	659.7
165°	569.3	572.6	576.0	586.0	593.8	600.5	608.4	618.4	627.3	635.1	643.0
167.5°	573.8	576.0	578.2	586.0	592.7	596.1	601.7	608.4	615.1	621.8	627.3
170°	576.0	577.6	579.3	584.9	590.5	592.7	596.1	600.5	606.1	609.5	613.9
172.5°	578.2	579.4	580.5	583.8	587.1	588.3	589.4	592.7	596.1	598.3	601.7
175°	579.3	579.9	580.5	582.7	584.9	583.8	584.9	586.0	589.4	590.5	591.6
177.5°	580.5	580.5	580.5	581.6	583.8	581.6	580.5	581.6	583.8	583.8	584.9
180°	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5

TEST NUMBER: P1010122

CATALOG NUMBER: S122RDIP-B675D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1358.9	1356.9	1351.0	1352.9	1350.0	1350.0	1348.0	1348.0	1348.0	1352.9	1350.0
5°	1284.8	1277.9	1271.0	1268.1	1265.1	1262.1	1262.1	1261.2	1270.0	1268.1	1276.0
7.5°	1193.1	1191.1	1177.3	1177.3	1172.3	1170.4	1175.3	1176.3	1177.3	1179.3	1184.2
10°	1111.2	1106.2	1086.5	1088.5	1085.5	1081.6	1084.5	1082.5	1089.5	1091.4	1089.5
12.5°	1014.5	1005.6	983.9	973.0	961.2	952.3	963.1	955.2	982.9	990.8	1012.5
15°	886.2	869.4	854.6	854.6	843.7	835.8	840.8	849.7	855.6	864.5	868.4
17.5°	800.3	793.4	781.6	774.7	771.7	768.7	768.7	772.7	785.5	784.5	792.4
20°	727.3	723.3	717.4	708.5	705.6	703.6	703.6	703.6	712.5	720.4	725.3
22.5°	677.0	674.0	670.1	658.2	652.3	650.3	655.2	658.2	665.1	671.0	676.0
25°	626.6	619.7	612.8	608.9	605.9	605.9	607.9	608.9	611.8	614.8	620.7
27.5°	585.2	580.3	570.4	559.5	559.5	556.6	558.5	560.5	567.4	577.3	582.2
30°	538.8	537.8	533.9	529.9	526.0	524.0	527.9	530.9	531.9	536.8	536.8
32.5°	505.3	498.3	491.4	487.5	485.5	484.5	485.5	489.5	489.5	495.4	502.3
35°	471.7	467.8	460.8	453.9	452.0	447.0	451.0	454.9	461.8	464.8	467.8
37.5°	435.2	430.3	427.3	425.3	421.4	422.4	419.4	425.3	431.2	430.3	432.2
40°	407.6	398.7	389.8	388.8	387.8	386.8	386.8	387.8	391.8	395.7	401.6
42.5°	372.0	369.1	361.2	353.3	351.3	349.3	347.4	351.3	359.2	366.1	369.1
45°	335.5	331.6	329.6	323.7	319.7	318.7	316.8	321.7	328.6	331.6	333.5
47.5°	302.0	301.0	295.1	296.0	293.1	294.1	293.1	296.0	296.0	299.0	301.0
50°	279.3	276.3	273.3	271.4	268.4	268.4	267.4	268.4	272.4	276.3	275.3
52.5°	256.6	251.6	250.7	249.7	247.7	249.7	246.7	247.7	251.6	253.6	252.6
55°	229.9	228.9	227.0	225.0	224.0	223.0	223.0	223.0	227.0	229.9	230.9
57.5°	209.2	204.3	200.3	200.3	196.4	195.4	197.4	198.4	201.3	203.3	205.3
60°	180.6	178.6	172.7	169.7	163.8	162.8	162.8	166.8	171.7	178.6	180.6
62.5°	150.0	147.0	146.0	146.0	146.0	146.0	146.0	146.0	146.0	147.0	147.0
65°	133.2	134.2	133.2	132.2	133.2	133.2	132.2	132.2	132.2	133.2	134.2
67.5°	119.4	118.4	119.4	118.4	117.4	117.4	116.4	117.4	118.4	119.4	119.4
70°	103.6	103.6	102.6	103.6	102.6	101.6	100.7	100.7	102.6	103.6	103.6
72.5°	88.8	88.8	87.8	87.8	85.9	85.9	86.8	85.9	85.9	88.8	88.8
75°	74.0	73.0	72.0	72.0	71.1	71.1	71.1	70.1	72.0	72.0	73.0
77.5°	58.2	58.2	58.2	57.2	57.2	56.2	56.2	57.2	57.2	57.2	58.2
80°	44.4	44.4	44.4	43.4	42.4	42.4	42.4	42.4	42.4	43.4	42.4
82.5°	30.6	30.6	30.6	30.6	30.6	29.6	29.6	29.6	30.6	30.6	29.6
85°	18.7	17.8	18.7	18.7	17.8	18.7	17.8	17.8	16.8	16.8	17.8
87.5°	7.9	6.9	5.9	5.9	6.9	5.9	5.9	5.9	6.9	5.9	5.9
90°	36.2	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.2
92.5°	79.2	74.8	73.7	69.2	70.3	68.1	70.3	69.2	73.7	74.8	79.2
95°	165.2	152.9	138.4	129.5	126.1	127.3	126.1	129.5	138.4	152.9	165.2
97.5°	331.5	298.0	254.5	232.2	219.9	213.2	219.9	232.2	254.5	298.0	331.5
100°	660.2	592.7	500.1	452.1	419.7	399.6	419.7	452.1	500.1	592.7	660.2
102.5°	1116.2	1043.7	941.0	850.6	808.2	779.1	808.2	850.6	941.0	1043.7	1116.2
105°	1478.5	1460.1	1390.8	1321.6	1273.6	1258.0	1273.6	1321.6	1390.8	1460.1	1478.5
107.5°	1609.6	1632.0	1630.8	1620.8	1606.3	1580.6	1606.3	1620.8	1630.8	1632.0	1609.6
110°	1588.4	1634.2	1682.2	1703.4	1713.4	1712.3	1713.4	1703.4	1682.2	1634.2	1588.4

TEST NUMBER: P1010122

CATALOG NUMBER: S122RDIP-B675D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1516.4	1570.6	1642.0	1681.1	1702.3	1710.1	1702.3	1681.1	1642.0	1570.6	1516.4
115°	1428.2	1485.7	1565.0	1616.3	1645.4	1655.4	1645.4	1616.3	1565.0	1485.7	1428.2
117.5°	1344.0	1398.7	1480.1	1534.8	1565.0	1572.8	1565.0	1534.8	1480.1	1398.7	1344.0
120°	1268.6	1319.4	1397.5	1450.0	1482.4	1493.5	1482.4	1450.0	1397.5	1319.4	1268.6
122.5°	1210.1	1254.7	1322.8	1374.1	1402.0	1410.9	1402.0	1374.1	1322.8	1254.7	1210.1
125°	1157.0	1198.9	1263.6	1306.0	1333.9	1342.8	1333.9	1306.0	1263.6	1198.9	1157.0
127.5°	1111.8	1150.9	1207.8	1248.0	1272.5	1279.2	1272.5	1248.0	1207.8	1150.9	1111.8
130°	1066.1	1102.9	1157.6	1195.5	1217.8	1226.8	1217.8	1195.5	1157.6	1102.9	1066.1
132.5°	1018.6	1052.6	1106.2	1144.2	1164.2	1172.1	1164.2	1144.2	1106.2	1052.6	1018.6
135°	972.2	1003.5	1051.5	1088.3	1108.4	1112.9	1108.4	1088.3	1051.5	1003.5	972.2
137.5°	925.4	953.3	999.0	1031.4	1049.3	1056.0	1049.3	1031.4	999.0	953.3	925.4
140°	884.0	908.6	944.3	973.4	990.1	996.8	990.1	973.4	944.3	908.6	884.0
142.5°	844.4	864.0	897.5	923.1	937.7	937.7	937.7	923.1	897.5	864.0	844.4
145°	812.1	828.3	855.0	874.0	885.2	888.5	885.2	874.0	855.0	828.3	812.1
147.5°	783.6	795.9	819.3	835.0	842.8	845.0	842.8	835.0	819.3	795.9	783.6
150°	759.0	769.1	785.8	799.2	805.9	807.0	805.9	799.2	785.8	769.1	759.0
152.5°	738.4	746.8	759.1	770.2	774.7	774.7	774.7	770.2	759.1	746.8	738.4
155°	718.3	724.4	736.7	744.5	749.0	746.8	749.0	744.5	736.7	724.4	718.3
157.5°	699.3	704.4	713.3	720.0	722.2	722.2	722.2	720.0	713.3	704.4	699.3
160°	680.3	684.3	692.1	697.7	698.8	698.8	698.8	697.7	692.1	684.3	680.3
162.5°	662.5	665.3	673.1	676.4	677.6	676.4	677.6	676.4	673.1	665.3	662.5
165°	645.2	647.4	651.9	656.4	656.4	655.2	656.4	656.4	651.9	647.4	645.2
167.5°	629.6	631.8	634.0	636.3	636.3	635.1	636.3	636.3	634.0	631.8	629.6
170°	615.0	616.2	617.3	620.6	619.5	617.3	619.5	620.6	617.3	616.2	615.0
172.5°	602.2	602.8	603.9	605.0	603.9	602.8	603.9	605.0	603.9	602.8	602.2
175°	592.2	592.7	592.7	593.8	592.7	590.5	592.7	593.8	592.7	592.7	592.2
177.5°	584.9	584.9	584.9	584.9	583.8	581.6	583.8	584.9	584.9	584.9	584.9
180°	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5

TEST NUMBER: P1010122

CATALOG NUMBER: S122RDIP-B675D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1352.9	1357.9	1355.9	1345.0	1355.9	1358.9	1364.8	1370.7	1374.6	1380.6	1385.5
5°	1268.1	1277.9	1283.9	1277.9	1297.7	1300.6	1314.4	1322.3	1334.2	1344.1	1351.9
7.5°	1188.1	1196.0	1207.9	1209.8	1221.7	1235.5	1255.2	1275.0	1293.7	1303.6	1312.5
10°	1102.3	1116.1	1133.9	1129.9	1147.7	1169.4	1190.1	1221.7	1237.5	1255.2	1271.0
12.5°	1016.4	1025.3	1049.0	1056.9	1082.5	1099.3	1127.9	1147.7	1187.1	1207.9	1221.7
15°	866.4	902.9	932.5	968.1	1001.6	1033.2	1058.9	1094.4	1128.9	1144.7	1167.4
17.5°	798.3	815.1	832.9	850.6	894.1	950.3	995.7	1034.2	1063.8	1084.5	1111.2
20°	727.3	744.1	763.8	780.6	807.2	847.7	903.9	970.0	1005.6	1027.3	1052.9
22.5°	677.0	692.7	705.6	720.4	741.1	770.7	813.1	895.0	942.4	969.1	991.8
25°	622.7	642.4	656.2	667.1	683.9	716.4	751.0	797.4	882.2	902.9	934.5
27.5°	585.2	591.1	606.9	623.7	640.4	658.2	693.7	733.2	790.4	835.8	874.3
30°	540.8	555.6	570.4	577.3	592.1	617.8	639.5	681.9	726.3	761.8	808.2
32.5°	507.2	516.1	526.0	542.8	556.6	574.3	596.0	631.6	669.1	691.8	727.3
35°	469.7	475.6	496.4	503.3	517.1	534.9	556.6	584.2	624.7	642.4	668.1
37.5°	434.2	448.0	453.9	469.7	482.6	500.3	516.1	547.7	574.3	595.1	618.7
40°	406.6	412.5	423.3	437.2	448.0	461.8	481.6	504.3	532.9	549.7	570.4
42.5°	373.0	378.0	391.8	399.7	417.4	430.3	442.1	469.7	495.4	508.2	528.9
45°	336.5	348.3	357.2	373.0	382.9	398.7	413.5	433.2	456.9	471.7	483.5
47.5°	304.9	316.8	325.7	340.5	356.2	363.2	378.9	399.7	421.4	433.2	450.0
50°	279.3	283.2	300.0	306.9	323.7	337.5	348.3	366.1	389.8	396.7	410.5
52.5°	254.6	257.6	268.4	277.3	292.1	303.9	317.8	334.5	354.3	365.1	376.0
55°	232.9	234.9	239.8	249.7	259.5	274.3	287.2	303.0	319.7	331.6	341.4
57.5°	208.2	212.2	216.1	222.0	231.9	245.7	259.5	274.3	288.2	296.0	308.9
60°	179.6	185.5	192.4	199.3	206.2	216.1	231.9	245.7	258.5	265.5	275.3
62.5°	149.0	160.9	166.8	174.7	180.6	189.5	201.3	217.1	226.0	234.9	242.8
65°	134.2	135.2	136.2	144.1	154.9	163.8	174.7	186.5	200.3	206.2	212.2
67.5°	119.4	120.4	122.4	123.4	127.3	137.2	149.0	161.8	172.7	176.6	182.6
70°	104.6	104.6	108.6	109.5	110.5	111.5	121.4	134.2	144.1	149.0	155.9
72.5°	88.8	89.8	91.8	92.8	94.7	96.7	99.7	106.6	118.4	123.4	131.2
75°	73.0	74.0	75.0	76.0	78.9	79.9	82.9	86.8	91.8	97.7	102.6
77.5°	58.2	58.2	59.2	61.2	63.2	64.1	67.1	69.1	71.1	74.0	78.0
80°	43.4	44.4	44.4	46.4	46.4	47.4	48.4	51.3	53.3	55.3	57.2
82.5°	29.6	31.6	31.6	31.6	32.6	33.6	34.5	34.5	36.5	37.5	40.5
85°	17.8	18.7	18.7	18.7	17.8	19.7	19.7	20.7	20.7	20.7	21.7
87.5°	6.9	5.9	6.9	6.9	6.9	7.9	6.9	6.9	7.9	8.9	8.9
90°	35.7	33.5	35.7	36.8	38.0	36.8	30.1	22.3	16.7	15.0	13.4
92.5°	83.7	96.0	112.7	144.0	171.9	169.7	131.7	89.3	59.2	53.0	46.9
95°	177.5	224.4	292.5	382.9	437.6	387.3	257.9	160.7	109.4	96.0	82.6
97.5°	365.0	477.8	598.3	718.9	713.3	551.4	342.7	207.6	141.8	126.7	111.6
100°	727.8	880.7	1019.1	1042.6	881.8	607.2	366.1	229.9	170.8	155.2	139.5
102.5°	1188.8	1290.4	1294.9	1163.1	887.4	586.0	367.2	250.0	196.5	180.8	165.2
105°	1496.9	1482.4	1356.2	1124.1	827.1	557.0	372.8	273.5	221.0	205.4	189.8
107.5°	1587.3	1477.9	1290.4	1041.5	771.3	541.4	385.1	296.9	245.6	230.0	214.3
110°	1542.7	1399.8	1200.0	964.4	733.4	536.9	400.7	320.4	271.2	255.0	238.9

TEST NUMBER: P1010122

CATALOG NUMBER: S122RDIP-B675D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1462.3	1307.1	1117.4	910.9	708.8	538.0	417.5	342.7	295.8	279.0	262.3
115°	1370.8	1224.5	1052.6	868.4	692.1	542.5	434.2	366.1	318.1	303.0	288.0
117.5°	1289.3	1153.1	999.0	839.4	683.1	549.2	452.1	387.3	342.7	327.0	311.4
120°	1217.8	1099.5	961.1	817.1	675.3	555.9	469.9	409.7	366.1	350.5	334.9
122.5°	1165.4	1054.9	931.0	798.1	670.9	563.7	485.6	430.9	390.7	374.5	358.3
125°	1115.1	1016.9	901.9	780.3	665.3	571.5	502.3	452.1	411.9	396.2	380.6
127.5°	1072.7	979.0	872.9	763.5	661.9	579.3	517.9	472.2	433.1	416.9	400.7
130°	1029.2	941.0	845.0	746.8	659.7	588.3	532.5	490.0	451.0	435.4	419.7
132.5°	984.5	905.3	818.2	733.4	658.6	597.2	547.0	505.7	468.8	453.2	437.6
135°	941.0	867.3	793.7	721.1	657.5	603.9	559.2	520.2	484.5	468.8	453.2
137.5°	897.5	837.2	773.6	712.2	657.5	610.6	569.3	532.5	496.7	482.2	467.7
140°	859.5	808.2	754.6	704.4	656.4	615.1	577.1	542.5	509.0	494.5	480.0
142.5°	824.9	782.5	739.0	696.5	656.4	618.4	583.8	550.3	517.9	504.6	491.2
145°	795.9	761.3	724.4	689.8	654.1	620.6	589.4	558.1	528.0	515.7	503.4
147.5°	771.3	743.4	713.3	683.1	650.8	621.8	592.7	564.8	535.8	524.6	513.5
150°	749.0	725.6	701.0	674.2	647.4	620.6	595.0	569.3	543.6	533.6	523.5
152.5°	730.0	711.1	688.7	666.4	641.8	618.4	596.1	573.8	551.4	542.5	533.6
155°	712.2	695.4	677.6	656.4	635.1	616.2	597.2	578.2	559.2	550.8	542.5
157.5°	694.3	679.8	664.2	647.4	628.4	611.7	597.2	581.6	564.8	557.6	550.3
160°	676.4	664.2	651.9	637.4	621.8	608.4	597.2	583.8	570.4	564.2	558.1
162.5°	659.7	649.7	639.6	628.4	616.2	605.0	596.1	584.9	573.8	569.3	564.8
165°	643.0	635.1	627.3	618.4	608.4	600.5	593.8	586.0	576.0	572.6	569.3
167.5°	627.3	621.8	615.1	608.4	601.7	596.1	592.7	586.0	578.2	576.0	573.8
170°	613.9	609.5	606.1	600.5	596.1	592.7	590.5	584.9	579.3	577.6	576.0
172.5°	601.7	598.3	596.1	592.7	589.4	588.3	587.1	583.8	580.5	579.4	578.2
175°	591.6	590.5	589.4	586.0	584.9	583.8	584.9	582.7	580.5	579.9	579.3
177.5°	584.9	583.8	583.8	581.6	580.5	581.6	583.8	581.6	580.5	580.5	580.5
180°	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5

TEST NUMBER: P1010122

CATALOG NUMBER: S122RDIP-B675D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1420.0	1420.0	1420.0	1420.0
2.5°	1394.4	1391.4	1409.2	1428.9
5°	1365.8	1370.7	1393.4	1421.0
7.5°	1336.2	1347.0	1373.7	1410.2
10°	1294.7	1314.4	1354.9	1392.4
12.5°	1254.3	1280.9	1319.4	1363.8
15°	1208.9	1238.5	1285.8	1339.1
17.5°	1158.5	1192.1	1247.3	1305.6
20°	1105.2	1149.6	1207.9	1271.0
22.5°	1046.0	1099.3	1159.5	1229.6
25°	988.8	1047.0	1107.2	1188.1
27.5°	932.5	989.8	1056.9	1138.8
30°	876.3	928.6	1000.6	1088.5
32.5°	816.1	870.4	946.4	1036.2
35°	760.8	815.1	886.2	975.0
37.5°	701.6	759.9	827.9	919.7
40°	632.6	700.6	766.8	854.6
42.5°	575.3	647.4	711.5	794.4
45°	529.9	598.0	651.3	732.2
47.5°	487.5	542.8	597.0	672.0
50°	447.0	489.5	545.7	612.8
52.5°	405.6	442.1	490.5	553.6
55°	368.1	402.6	446.0	494.4
57.5°	333.5	358.2	401.6	445.1
60°	295.1	320.7	354.3	390.8
62.5°	262.5	282.2	313.8	344.4
65°	228.0	246.7	270.4	299.0
67.5°	196.4	213.2	231.9	254.6
70°	167.8	180.6	194.4	214.1
72.5°	137.2	151.0	163.8	179.6
75°	112.5	118.4	129.3	140.1
77.5°	86.8	94.7	100.7	109.5
80°	62.2	69.1	71.1	78.0
82.5°	41.4	45.4	49.3	51.3
85°	23.7	25.7	29.6	30.6
87.5°	8.9	9.9	11.8	13.8
90°	11.2	8.9	4.5	1.1
92.5°	38.0	32.4	23.4	16.7
95°	64.7	54.7	43.5	39.1
97.5°	91.5	77.0	64.7	58.0
100°	117.2	99.3	89.3	86.0
102.5°	141.8	123.9	113.9	111.6
105°	165.2	148.5	140.6	136.2
107.5°	189.8	174.1	166.3	163.0
110°	215.4	200.9	194.2	189.8

TEST NUMBER: P1010122

CATALOG NUMBER: S122RDIP-B675D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	240.0	226.6	218.8	214.3
115°	265.7	252.3	245.6	240.0
117.5°	290.2	277.9	271.2	266.8
120°	312.6	302.5	295.8	291.3
122.5°	336.0	324.8	318.1	314.8
125°	358.3	344.9	338.2	334.9
127.5°	379.5	365.0	356.1	351.6
130°	397.4	381.8	370.6	366.1
132.5°	414.1	397.4	385.1	379.5
135°	427.5	410.8	397.4	392.9
137.5°	442.0	424.2	410.8	405.2
140°	455.4	437.6	424.2	419.7
142.5°	467.7	449.8	437.6	434.2
145°	481.1	464.4	453.2	448.7
147.5°	494.5	478.9	467.7	464.4
150°	506.8	492.3	483.3	480.0
152.5°	517.9	505.7	496.7	495.6
155°	530.2	517.9	511.2	510.1
157.5°	540.3	529.1	523.5	522.4
160°	549.2	540.3	535.8	534.7
162.5°	557.0	550.3	545.8	547.0
165°	563.7	557.0	554.8	555.9
167.5°	569.3	564.8	562.6	563.7
170°	573.8	570.4	569.3	571.5
172.5°	577.1	573.8	574.9	576.0
175°	579.3	577.1	578.2	579.3
177.5°	580.5	578.2	579.3	581.6
180°	580.5	580.5	580.5	580.5

(END OF REPORT)