

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010146

Luminaire Tested: S122RDIP-B675D330UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010146
REPORT IS A COMBINATION OF REPORTS P988488 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B675D330UB40-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3819.0 lumens
Efficiency: N/A
Efficacy: 84.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010146

CATALOG NUMBER: S122RDIP-B675D330UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1010146

CATALOG NUMBER: S122RDIP-B675D330UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71	66		
1	102	98	95	92	96	93	90	87	83	80	78	73	72	70	65	63	62	58		
2	94	87	82	77	89	83	78	73	74	70	67	66	63	60	58	56	54	50		
3	87	78	71	65	82	74	68	63	66	61	57	59	55	52	53	50	47	44		
4	80	70	62	56	75	66	60	54	60	54	50	54	49	46	48	45	42	39		
5	74	63	55	49	70	60	53	48	54	48	44	49	44	41	44	40	37	35		
6	69	57	49	44	65	54	47	42	49	44	39	45	40	36	40	37	34	31		
7	64	52	44	39	60	50	43	38	45	39	35	41	36	33	37	33	30	28		
8	60	48	40	35	56	46	39	34	42	36	32	38	33	30	34	31	28	26		
9	56	44	37	32	53	42	35	31	39	33	29	35	31	27	32	28	25	23		
10	53	41	34	29	50	39	33	28	36	30	27	33	28	25	30	26	23	22		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23247	23247	23247	23247
5°	23302	24693	23383	19726
10°	23046	26100	23209	16290
15°	22546	26107	22927	12237
20°	21943	21581	22421	10097
25°	21215	13485	21672	8588
30°	20283	8634	20834	7394
35°	19151	6635	19770	6327
40°	17887	5577	18652	5535
45°	16539	4747	17230	4647
50°	15156	4033	15864	4019
55°	13624	3505	14360	3460
60°	12265	2672	12915	2641
65°	10992	2012	11646	2282
70°	9593	1606	10342	1859
75°	8106	1231	8850	1407
80°	6435	837	6930	923
85°	4464	433	4902	456

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 21267 cd/sqm

TEST NUMBER: P1010146

CATALOG NUMBER: S122RDIP-B675D330UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.3	3.6
10°-20°	388.8	10.2
20°-30°	500.4	13.1
30°-40°	474.7	12.4
40°-50°	406.9	10.7
50°-60°	309.9	8.1
60°-70°	195.4	5.1
70°-80°	97.5	2.6
80°-90°	26.2	0.7
90°-100°	71.6	1.9
100°-110°	252.3	6.6
110°-120°	265.0	6.9
120°-130°	218.0	5.7
130°-140°	175.1	4.6
140°-150°	132.3	3.5
150°-160°	93.0	2.4
160°-170°	54.7	1.4
170°-180°	17.8	0.5
0°-30°	1028.6	26.9
0°-40°	1503.3	39.4
0°-60°	2220.0	58.1
0°-90°	2539.2	66.5
90°-120°	588.9	15.4
90°-150°	1114.3	29.2
90°-180°	1280.0	33.5
0°-180°	3819.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1469	1469	1469	1469	1469	
5°	1470	1634	1475	1305	1470	139
15°	1385	1844	1408	864	1385	390
25°	1229	984	1255	627	1229	564
35°	1008	485	1041	462	1008	631
45°	757	337	789	330	757	585
55°	511	234	539	231	511	461
65°	309	122	328	138	309	307
75°	145	64	158	74	145	157
85°	32	18	35	19	32	36
90°	0	12	0	12	0	3
95°	12	40	12	40	12	13
105°	43	398	43	398	43	46
115°	76	524	76	524	76	75
125°	106	425	106	425	106	94
135°	124	352	124	352	124	96
145°	142	281	142	281	142	89
155°	162	236	162	236	162	74
165°	176	208	176	208	176	50
175°	183	187	183	187	183	17
180°	184	184	184	184	184	

TEST NUMBER: P1010146

CATALOG NUMBER: S122RDIP-B675D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6
2.5°	1477.8	1484.0	1487.0	1491.1	1500.3	1506.4	1515.6	1517.6	1516.6	1520.7	1509.5
5°	1469.7	1482.9	1495.2	1505.4	1521.7	1531.9	1543.1	1556.4	1559.5	1574.8	1565.6
7.5°	1458.4	1477.8	1495.2	1515.6	1540.1	1553.4	1570.7	1591.1	1600.3	1618.7	1623.8
10°	1440.1	1467.6	1497.2	1518.7	1552.3	1575.8	1592.1	1624.8	1646.2	1673.8	1669.7
12.5°	1410.5	1446.2	1486.0	1521.7	1565.6	1580.9	1611.5	1645.2	1672.8	1698.3	1720.7
15°	1385.0	1425.8	1469.7	1513.6	1563.6	1592.1	1622.8	1666.6	1696.2	1741.1	1760.5
17.5°	1350.3	1402.3	1454.4	1503.3	1562.5	1595.2	1633.0	1675.8	1719.7	1762.6	1777.9
20°	1314.5	1370.7	1426.8	1493.1	1560.5	1592.1	1630.9	1684.0	1726.9	1760.5	1760.5
22.5°	1271.7	1340.0	1404.3	1467.6	1541.1	1587.0	1626.8	1689.1	1719.7	1726.9	1699.3
25°	1228.8	1297.2	1367.6	1446.2	1529.9	1570.7	1615.6	1673.8	1684.0	1655.4	1584.0
27.5°	1177.8	1254.3	1333.9	1418.6	1506.4	1557.4	1598.3	1637.0	1617.7	1541.1	1429.9
30°	1125.7	1208.4	1298.2	1378.8	1485.0	1531.9	1566.6	1577.8	1516.6	1392.1	1248.2
32.5°	1071.6	1152.3	1247.2	1344.1	1451.3	1496.2	1518.7	1489.1	1376.8	1219.6	1044.1
35°	1008.4	1099.2	1198.2	1299.2	1405.4	1439.0	1452.3	1379.9	1235.9	1032.8	858.3
37.5°	951.2	1042.0	1148.2	1251.3	1354.3	1372.7	1359.4	1246.2	1063.5	862.4	692.0
40°	883.8	980.8	1084.9	1200.2	1284.9	1290.0	1257.4	1110.4	883.8	695.0	589.9
42.5°	821.6	919.6	1023.7	1141.0	1205.3	1188.0	1144.1	951.2	737.9	599.1	514.4
45°	757.3	850.2	962.4	1066.5	1112.5	1071.6	1005.3	800.2	619.5	515.4	450.1
47.5°	695.0	781.8	893.0	993.0	1001.2	955.3	876.7	670.5	536.8	453.1	400.1
50°	633.8	720.5	824.6	907.3	899.1	835.9	747.1	582.8	466.4	400.1	356.2
52.5°	572.6	651.1	752.2	817.5	782.8	721.6	633.8	494.0	407.2	349.0	315.4
55°	511.3	584.8	671.6	725.6	670.5	600.1	537.9	423.5	353.1	306.2	280.7
57.5°	460.3	518.5	598.1	630.7	564.4	509.3	455.2	364.4	306.2	272.5	242.9
60°	404.2	457.2	522.5	541.9	473.6	428.7	382.7	308.2	262.3	232.7	213.3
62.5°	356.2	400.1	450.1	450.1	389.9	356.2	321.5	258.2	220.4	197.0	187.8
65°	309.2	340.9	376.6	372.5	321.5	291.9	264.3	213.3	184.7	168.4	159.2
67.5°	263.3	287.8	311.3	297.0	260.3	234.7	209.2	172.5	153.1	141.9	129.6
70°	221.5	240.9	253.1	239.8	203.1	181.7	163.3	138.8	123.5	109.2	102.1
72.5°	185.7	193.9	198.0	181.7	151.0	138.8	125.5	108.2	94.9	87.8	85.7
75°	144.9	152.1	149.0	136.8	111.2	102.1	91.9	79.6	76.5	72.5	70.4
77.5°	113.3	113.3	108.2	97.0	79.6	72.5	68.4	62.3	59.2	58.2	56.1
80°	80.6	79.6	76.5	64.3	54.1	50.0	50.0	45.9	44.9	42.9	42.9
82.5°	53.1	53.1	49.0	38.8	35.7	34.7	33.7	31.6	31.6	30.6	30.6
85°	31.6	29.6	24.5	21.4	20.4	20.4	19.4	18.4	19.4	18.4	18.4
87.5°	14.3	11.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2
90°	0.4	1.4	2.8	3.5	4.2	4.8	5.3	7.1	9.5	11.7	12.0
92.5°	5.3	7.4	10.2	12.0	14.8	16.8	18.7	28.3	41.7	53.7	54.4
95°	12.4	13.8	17.3	20.5	26.2	30.4	34.6	50.9	81.6	122.6	138.5
97.5°	18.4	20.5	24.4	29.0	35.3	40.1	44.9	65.7	108.5	174.6	225.8
100°	27.2	28.3	31.5	37.1	44.2	49.2	54.1	72.8	115.9	192.3	279.2
102.5°	35.3	36.0	39.2	44.9	52.3	57.2	62.2	79.2	116.3	185.5	281.0
105°	43.1	44.5	47.0	52.3	60.1	65.0	70.0	86.6	118.0	176.4	261.9
107.5°	51.6	52.7	55.1	60.1	67.9	72.8	77.8	94.0	121.9	171.4	244.2
110°	60.1	61.5	63.6	68.2	75.6	80.8	85.9	101.4	126.9	170.0	232.2

TEST NUMBER: P1010146

CATALOG NUMBER: S122RDIP-B675D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	67.9	69.3	71.7	76.0	83.1	88.4	93.7	108.5	132.2	170.3	224.4
115°	76.0	77.8	79.9	84.1	91.2	96.0	100.7	115.9	137.5	171.8	219.1
117.5°	84.5	85.9	88.0	91.9	98.6	103.6	108.5	122.6	143.1	173.9	216.3
120°	92.2	93.7	95.8	99.0	106.0	111.0	115.9	129.7	148.8	176.0	213.8
122.5°	99.7	100.7	102.8	106.4	113.4	118.6	123.7	136.4	153.7	178.5	212.4
125°	106.0	107.1	109.2	113.4	120.5	125.4	130.4	143.1	159.0	180.9	210.6
127.5°	111.3	112.7	115.6	120.2	126.9	132.0	137.1	149.5	164.0	183.4	209.6
130°	115.9	117.3	120.9	125.8	132.9	137.9	142.8	155.1	168.6	186.2	208.9
132.5°	120.2	121.9	125.8	131.1	138.5	143.4	148.4	160.1	173.2	189.1	208.5
135°	124.4	125.8	130.1	135.4	143.5	148.4	153.4	164.7	177.1	191.2	208.2
137.5°	128.3	130.1	134.3	140.0	148.1	152.7	157.3	168.6	180.2	193.3	208.2
140°	132.9	134.3	138.5	144.2	152.0	156.6	161.2	171.8	182.7	194.7	207.8
142.5°	137.5	138.5	142.4	148.1	155.5	159.8	164.0	174.2	184.8	195.8	207.8
145°	142.1	143.5	147.0	152.3	159.4	163.3	167.2	176.7	186.6	196.5	207.1
147.5°	147.0	148.1	151.6	156.6	162.6	166.1	169.6	178.8	187.7	196.9	206.0
150°	152.0	153.0	155.9	160.5	165.8	169.0	172.1	180.2	188.4	196.5	205.0
152.5°	156.9	157.3	160.1	164.0	168.9	171.8	174.6	181.7	188.7	195.8	203.2
155°	161.5	161.9	164.0	167.9	171.8	174.4	177.1	183.1	189.1	195.1	201.1
157.5°	165.4	165.8	167.5	171.1	174.2	176.5	178.8	184.1	189.1	193.7	199.0
160°	169.3	169.6	171.1	173.9	176.7	178.6	180.6	184.8	189.1	192.6	196.9
162.5°	173.2	172.8	174.2	176.4	178.8	180.2	181.7	185.2	188.7	191.6	195.1
165°	176.0	175.6	176.4	178.5	180.2	181.3	182.4	185.5	188.0	190.1	192.6
167.5°	178.5	178.1	178.8	180.2	181.7	182.4	183.1	185.5	187.7	188.7	190.5
170°	180.9	180.2	180.6	181.7	182.4	182.9	183.4	185.2	187.0	187.7	188.7
172.5°	182.4	182.0	181.7	182.7	183.1	183.4	183.8	184.8	185.9	186.2	186.6
175°	183.4	183.1	182.7	183.4	183.4	183.6	183.8	184.5	185.2	184.8	185.2
177.5°	184.1	183.4	183.1	183.8	183.8	183.8	183.8	184.1	184.8	184.1	183.8
180°	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8

TEST NUMBER: P1010146

CATALOG NUMBER: S122RDIP-B675D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6
2.5°	1520.7	1522.7	1525.8	1540.1	1542.1	1546.2	1544.2	1544.2	1545.2	1543.1	1544.2
5°	1586.0	1589.1	1604.4	1621.7	1625.8	1621.7	1626.8	1634.0	1634.0	1634.0	1631.9
7.5°	1647.2	1658.5	1675.8	1701.3	1706.4	1711.5	1720.7	1714.6	1716.7	1725.8	1722.8
10°	1706.4	1722.8	1742.2	1763.6	1774.8	1782.0	1786.1	1795.2	1816.7	1792.2	1801.4
12.5°	1762.6	1786.1	1806.5	1829.9	1838.1	1847.3	1850.3	1858.5	1858.5	1857.5	1864.6
15°	1799.3	1820.8	1839.1	1854.4	1856.5	1854.4	1852.4	1853.4	1856.5	1844.2	1851.4
17.5°	1807.5	1809.5	1815.6	1809.5	1810.5	1789.1	1776.9	1773.8	1745.2	1746.2	1769.7
20°	1767.7	1733.0	1723.8	1690.1	1669.7	1614.6	1612.5	1597.2	1537.0	1555.4	1551.3
22.5°	1658.5	1599.3	1520.7	1481.9	1462.5	1404.3	1359.4	1327.8	1306.4	1284.9	1275.8
25°	1514.6	1418.6	1307.4	1230.8	1219.6	1165.5	1082.9	1044.1	998.1	983.9	1008.4
27.5°	1328.8	1204.3	1078.8	961.4	940.0	891.0	849.1	821.6	768.5	765.5	767.5
30°	1076.7	951.2	846.1	769.5	716.5	694.0	666.5	646.0	624.6	632.8	634.8
32.5°	884.9	765.5	667.5	626.6	602.2	587.9	564.4	551.1	541.9	538.9	537.9
35°	703.2	623.6	579.7	539.9	525.6	515.4	498.1	491.9	483.8	484.8	484.8
37.5°	602.2	535.8	503.2	482.7	469.5	464.4	453.1	447.0	441.9	439.9	442.9
40°	519.5	473.6	453.1	434.8	423.5	421.5	415.4	408.2	402.1	403.1	406.2
42.5°	459.3	432.7	408.2	394.0	385.8	382.7	377.6	372.5	372.5	369.5	368.4
45°	411.3	389.9	369.5	356.2	351.1	347.0	340.9	339.9	335.8	336.8	337.8
47.5°	368.4	351.1	335.8	322.5	317.4	316.4	310.3	306.2	306.2	305.2	304.1
50°	329.7	312.3	299.0	291.9	284.7	282.7	281.7	280.7	278.6	278.6	279.6
52.5°	298.0	280.7	270.5	264.3	260.3	258.2	258.2	257.2	257.2	257.2	256.2
55°	263.3	249.0	240.9	238.8	236.8	235.8	234.7	232.7	231.7	233.7	231.7
57.5°	230.7	225.6	218.4	216.4	211.3	211.3	208.2	206.2	204.1	206.2	206.2
60°	205.1	198.0	193.9	187.8	183.7	179.6	174.5	173.5	171.5	170.4	169.4
62.5°	178.6	172.5	162.3	153.1	147.0	142.9	140.8	139.8	139.8	138.8	138.8
65°	149.0	134.7	129.6	126.6	125.5	124.5	122.5	121.5	122.5	121.5	122.5
67.5°	116.3	114.3	111.2	109.2	108.2	107.2	107.2	106.1	106.1	106.1	106.1
70°	101.0	95.9	94.9	92.9	92.9	91.9	91.9	91.9	91.9	90.8	92.9
72.5°	83.7	80.6	79.6	78.6	78.6	78.6	77.6	77.6	77.6	76.5	77.6
75°	68.4	67.4	65.3	65.3	64.3	65.3	64.3	64.3	63.3	64.3	64.3
77.5°	55.1	54.1	53.1	53.1	52.1	52.1	52.1	52.1	52.1	52.1	53.1
80°	41.8	40.8	39.8	40.8	39.8	40.8	39.8	39.8	40.8	39.8	39.8
82.5°	30.6	29.6	29.6	28.6	28.6	28.6	28.6	28.6	28.6	28.6	28.6
85°	18.4	17.4	17.4	18.4	17.4	18.4	17.4	17.4	17.4	18.4	18.4
87.5°	8.2	9.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	9.2
90°	11.7	11.3	10.6	11.3	11.5	11.7	11.7	11.7	11.7	11.7	11.7
92.5°	45.6	35.7	30.4	26.5	25.1	23.7	23.3	21.9	22.3	21.6	22.3
95°	121.2	92.6	71.0	56.2	52.3	48.4	43.8	41.0	39.9	40.3	39.9
97.5°	227.6	189.4	151.3	115.6	105.0	94.4	80.6	73.5	69.6	67.5	69.6
100°	330.1	322.7	278.8	230.4	209.0	187.7	158.3	143.1	132.9	126.5	132.9
102.5°	368.3	410.0	408.5	376.4	353.4	330.4	297.9	269.3	255.9	246.7	255.9
105°	355.9	429.4	469.3	473.9	468.1	462.3	440.4	418.4	403.2	398.3	403.2
107.5°	329.7	408.5	467.9	502.6	509.6	516.7	516.3	513.2	508.6	500.4	508.6
110°	305.4	379.9	443.2	488.4	502.9	517.4	532.6	539.3	542.5	542.1	542.5

TEST NUMBER: P1010146

CATALOG NUMBER: S122RDIP-B675D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	288.4	353.8	413.8	463.0	480.2	497.3	519.9	532.2	539.0	541.4	539.0
115°	275.0	333.3	387.7	434.0	452.2	470.4	495.5	511.7	520.9	524.1	520.9
117.5°	265.8	316.3	365.1	408.2	425.5	442.8	468.6	485.9	495.5	498.0	495.5
120°	258.7	304.3	348.1	385.6	401.6	417.7	442.5	459.1	469.3	472.9	469.3
122.5°	252.7	294.7	334.0	369.0	383.1	397.2	418.8	435.1	443.9	446.7	443.9
125°	247.0	285.6	322.0	353.1	366.4	379.6	400.1	413.5	422.3	425.2	422.3
127.5°	241.7	276.4	309.9	339.6	352.0	364.4	382.4	395.1	402.9	405.0	402.9
130°	236.4	267.5	297.9	325.8	337.5	349.2	366.5	378.5	385.6	388.4	385.6
132.5°	232.2	259.1	286.6	311.7	322.5	333.3	350.2	362.3	368.6	371.1	368.6
135°	228.3	251.3	274.6	297.9	307.8	317.7	332.9	344.6	350.9	352.4	350.9
137.5°	225.5	244.9	265.1	284.1	293.0	301.8	316.3	326.6	332.2	334.3	332.2
140°	223.0	238.9	255.9	272.1	279.9	287.7	299.0	308.2	313.5	315.6	313.5
142.5°	220.5	234.0	247.7	261.2	267.4	273.5	284.1	292.3	296.9	296.9	296.9
145°	218.4	229.4	241.0	252.0	257.1	262.2	270.7	276.7	280.3	281.3	280.3
147.5°	216.3	225.8	235.4	244.2	248.1	252.0	259.4	264.4	266.8	267.5	266.8
150°	213.5	221.9	229.7	237.1	240.3	243.5	248.8	253.0	255.2	255.5	255.2
152.5°	211.0	218.1	225.1	231.1	233.8	236.4	240.3	243.9	245.3	245.3	245.3
155°	207.8	214.5	220.2	225.5	227.4	229.4	233.3	235.7	237.1	236.4	237.1
157.5°	205.0	210.3	215.2	219.8	221.4	223.0	225.8	228.0	228.7	228.7	228.7
160°	201.8	206.4	210.3	214.2	215.4	216.6	219.1	220.9	221.2	221.2	221.2
162.5°	199.0	202.5	205.7	208.9	209.8	210.6	213.1	214.2	214.5	214.2	214.5
165°	195.8	198.6	201.1	203.6	204.3	205.0	206.4	207.8	207.8	207.5	207.8
167.5°	192.6	194.7	196.9	198.6	199.3	200.0	200.7	201.4	201.4	201.1	201.4
170°	190.1	191.9	193.0	194.4	194.8	195.1	195.4	196.5	196.1	195.4	196.1
172.5°	187.7	188.7	189.4	190.5	190.6	190.8	191.2	191.6	191.2	190.8	191.2
175°	185.5	186.6	187.0	187.3	187.5	187.7	187.7	188.0	187.7	187.0	187.7
177.5°	184.1	184.8	184.8	185.2	185.2	185.2	185.2	185.2	184.8	184.1	184.8
180°	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8

TEST NUMBER: P1010146

CATALOG NUMBER: S122RDIP-B675D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6
2.5°	1548.3	1541.1	1539.1	1541.1	1539.1	1540.1	1532.9	1506.4	1513.6	1502.3	1508.4
5°	1636.0	1629.9	1616.6	1614.6	1612.5	1610.5	1600.3	1576.8	1567.6	1552.3	1551.3
7.5°	1719.7	1719.7	1709.5	1702.4	1693.2	1686.0	1672.8	1638.1	1623.8	1605.4	1595.2
10°	1802.4	1775.8	1787.1	1779.9	1757.5	1753.4	1728.9	1708.5	1680.9	1662.6	1646.2
12.5°	1861.6	1853.4	1843.2	1837.1	1831.0	1817.7	1801.4	1749.3	1735.0	1698.3	1679.9
15°	1859.5	1854.4	1857.5	1857.5	1855.5	1852.4	1839.1	1801.4	1776.9	1741.1	1709.5
17.5°	1759.5	1772.8	1786.1	1795.2	1815.6	1824.8	1837.1	1814.6	1799.3	1768.7	1735.0
20°	1585.0	1617.7	1656.4	1664.6	1683.0	1737.1	1761.6	1780.9	1787.1	1776.9	1749.3
22.5°	1342.1	1369.6	1463.5	1461.5	1488.0	1552.3	1623.8	1682.0	1727.9	1753.4	1743.2
25°	1051.2	1090.0	1140.0	1177.8	1264.5	1360.5	1449.3	1542.1	1621.7	1692.2	1709.5
27.5°	795.0	846.1	885.9	935.9	979.8	1093.1	1207.4	1352.3	1445.2	1578.9	1648.3
30°	643.0	666.5	706.3	729.7	751.2	837.9	967.5	1110.4	1273.7	1427.8	1547.2
32.5°	549.1	565.4	595.0	605.2	627.7	685.8	767.5	898.1	1066.5	1253.3	1410.5
35°	493.0	510.3	516.4	525.6	544.0	580.7	636.9	731.8	883.8	1066.5	1254.3
37.5°	445.0	454.2	471.5	477.6	483.8	511.3	549.1	615.4	716.5	866.5	1074.7
40°	411.3	416.4	425.6	430.7	434.8	454.2	487.8	532.8	607.3	721.6	913.4
42.5°	375.6	381.7	387.8	394.0	399.1	414.4	434.8	477.6	527.7	614.4	753.2
45°	340.9	345.0	352.1	356.2	363.3	375.6	394.0	423.5	468.5	523.6	635.8
47.5°	309.2	314.3	317.4	322.5	327.6	340.9	358.2	377.6	414.4	468.5	550.1
50°	280.7	286.8	290.9	291.9	296.0	308.2	322.5	343.9	367.4	409.3	480.7
52.5°	260.3	261.3	264.3	268.4	267.4	274.5	287.8	304.1	328.6	362.3	414.4
55°	236.8	239.8	241.9	242.9	242.9	249.0	256.2	271.5	290.9	318.4	362.3
57.5°	207.2	210.2	216.4	218.4	221.5	224.5	227.6	237.8	254.1	280.7	316.4
60°	176.6	178.6	184.7	188.8	190.9	199.0	203.1	211.3	220.4	239.8	273.5
62.5°	141.9	143.9	147.0	151.0	155.1	167.4	177.6	185.7	192.9	206.2	233.7
65°	123.5	124.5	126.6	127.6	128.6	133.7	142.9	154.1	167.4	177.6	193.9
67.5°	107.2	108.2	109.2	111.2	112.3	113.3	117.4	120.4	133.7	148.0	160.2
70°	91.9	93.9	94.9	94.9	95.9	98.0	100.0	104.1	108.2	115.3	130.6
72.5°	77.6	78.6	80.6	80.6	80.6	82.7	84.7	86.8	88.8	92.9	99.0
75°	64.3	66.3	66.3	66.3	67.4	67.4	69.4	71.4	73.5	76.5	78.6
77.5°	53.1	53.1	53.1	53.1	54.1	54.1	55.1	57.2	58.2	59.2	61.2
80°	39.8	40.8	40.8	40.8	41.8	41.8	41.8	43.9	44.9	44.9	46.9
82.5°	29.6	29.6	29.6	30.6	29.6	30.6	30.6	31.6	30.6	31.6	32.7
85°	18.4	18.4	18.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4	20.4
87.5°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	10.2	9.2	9.2
90°	11.7	11.7	11.7	11.5	11.3	10.6	11.3	11.7	12.0	11.7	9.5
92.5°	21.9	23.3	23.7	25.1	26.5	30.4	35.7	45.6	54.4	53.7	41.7
95°	41.0	43.8	48.4	52.3	56.2	71.0	92.6	121.2	138.5	122.6	81.6
97.5°	73.5	80.6	94.4	105.0	115.6	151.3	189.4	227.6	225.8	174.6	108.5
100°	143.1	158.3	187.7	209.0	230.4	278.8	322.7	330.1	279.2	192.3	115.9
102.5°	269.3	297.9	330.4	353.4	376.4	408.5	410.0	368.3	281.0	185.5	116.3
105°	418.4	440.4	462.3	468.1	473.9	469.3	429.4	355.9	261.9	176.4	118.0
107.5°	513.2	516.3	516.7	509.6	502.6	467.9	408.5	329.7	244.2	171.4	121.9
110°	539.3	532.6	517.4	502.9	488.4	443.2	379.9	305.4	232.2	170.0	126.9

TEST NUMBER: P1010146

CATALOG NUMBER: S122RDIP-B675D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	532.2	519.9	497.3	480.2	463.0	413.8	353.8	288.4	224.4	170.3	132.2
115°	511.7	495.5	470.4	452.2	434.0	387.7	333.3	275.0	219.1	171.8	137.5
117.5°	485.9	468.6	442.8	425.5	408.2	365.1	316.3	265.8	216.3	173.9	143.1
120°	459.1	442.5	417.7	401.6	385.6	348.1	304.3	258.7	213.8	176.0	148.8
122.5°	435.1	418.8	397.2	383.1	369.0	334.0	294.7	252.7	212.4	178.5	153.7
125°	413.5	400.1	379.6	366.4	353.1	322.0	285.6	247.0	210.6	180.9	159.0
127.5°	395.1	382.4	364.4	352.0	339.6	309.9	276.4	241.7	209.6	183.4	164.0
130°	378.5	366.5	349.2	337.5	325.8	297.9	267.5	236.4	208.9	186.2	168.6
132.5°	362.3	350.2	333.3	322.5	311.7	286.6	259.1	232.2	208.5	189.1	173.2
135°	344.6	332.9	317.7	307.8	297.9	274.6	251.3	228.3	208.2	191.2	177.1
137.5°	326.6	316.3	301.8	293.0	284.1	265.1	244.9	225.5	208.2	193.3	180.2
140°	308.2	299.0	287.7	279.9	272.1	255.9	238.9	223.0	207.8	194.7	182.7
142.5°	292.3	284.1	273.5	267.4	261.2	247.7	234.0	220.5	207.8	195.8	184.8
145°	276.7	270.7	262.2	257.1	252.0	241.0	229.4	218.4	207.1	196.5	186.6
147.5°	264.4	259.4	252.0	248.1	244.2	235.4	225.8	216.3	206.0	196.9	187.7
150°	253.0	248.8	243.5	240.3	237.1	229.7	221.9	213.5	205.0	196.5	188.4
152.5°	243.9	240.3	236.4	233.8	231.1	225.1	218.1	211.0	203.2	195.8	188.7
155°	235.7	233.3	229.4	227.4	225.5	220.2	214.5	207.8	201.1	195.1	189.1
157.5°	228.0	225.8	223.0	221.4	219.8	215.2	210.3	205.0	199.0	193.7	189.1
160°	220.9	219.1	216.6	215.4	214.2	210.3	206.4	201.8	196.9	192.6	189.1
162.5°	214.2	213.1	210.6	209.8	208.9	205.7	202.5	199.0	195.1	191.6	188.7
165°	207.8	206.4	205.0	204.3	203.6	201.1	198.6	195.8	192.6	190.1	188.0
167.5°	201.4	200.7	200.0	199.3	198.6	196.9	194.7	192.6	190.5	188.7	187.7
170°	196.5	195.4	195.1	194.8	194.4	193.0	191.9	190.1	188.7	187.7	187.0
172.5°	191.6	191.2	190.8	190.6	190.5	189.4	188.7	187.7	186.6	186.2	185.9
175°	188.0	187.7	187.7	187.5	187.3	187.0	186.6	185.5	185.2	184.8	185.2
177.5°	185.2	185.2	185.2	185.2	185.2	184.8	184.8	184.1	183.8	184.1	184.8
180°	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8

TEST NUMBER: P1010146

CATALOG NUMBER: S122RDIP-B675D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6
2.5°	1499.3	1494.2	1494.2	1491.1	1491.1	1474.8	1474.8	1479.9	1473.7	1466.6	1456.4
5°	1538.0	1526.8	1523.8	1519.7	1506.4	1486.0	1477.8	1474.8	1462.5	1447.2	1429.9
7.5°	1574.8	1556.4	1547.2	1538.0	1520.7	1492.1	1475.8	1464.6	1446.2	1422.7	1400.3
10°	1610.5	1587.0	1563.6	1552.3	1527.8	1492.1	1468.6	1450.3	1423.7	1392.1	1360.5
12.5°	1643.2	1594.2	1590.1	1567.6	1531.9	1491.1	1455.4	1428.8	1395.2	1358.4	1321.7
15°	1671.7	1621.7	1597.2	1576.8	1529.9	1478.9	1441.1	1408.4	1363.5	1321.7	1276.8
17.5°	1686.0	1631.9	1615.6	1581.9	1534.0	1467.6	1416.6	1376.8	1327.8	1277.8	1226.8
20°	1700.3	1637.0	1610.5	1587.0	1521.7	1446.2	1389.0	1343.1	1289.0	1229.8	1173.7
22.5°	1707.5	1637.0	1605.4	1572.7	1509.5	1422.7	1355.4	1301.3	1238.0	1177.8	1110.4
25°	1695.2	1630.9	1593.2	1559.5	1488.0	1394.1	1316.6	1255.3	1188.0	1119.6	1051.2
27.5°	1664.6	1616.6	1572.7	1538.0	1458.4	1357.4	1275.8	1206.4	1136.9	1060.4	991.0
30°	1607.4	1586.0	1551.3	1512.5	1425.8	1324.7	1227.8	1156.3	1079.8	1003.3	930.8
32.5°	1518.7	1537.0	1514.6	1480.9	1387.0	1279.8	1176.8	1104.3	1020.6	937.9	871.6
35°	1410.5	1475.8	1463.5	1440.1	1346.2	1231.9	1128.8	1041.0	957.3	873.6	807.3
37.5°	1292.1	1391.1	1401.3	1387.0	1299.2	1182.9	1069.6	983.9	898.1	813.4	746.1
40°	1129.8	1281.9	1314.5	1320.7	1250.2	1123.7	1005.3	921.6	836.9	754.2	672.6
42.5°	980.8	1172.7	1213.5	1239.0	1188.0	1065.5	946.1	853.2	769.5	695.0	613.4
45°	841.0	1041.0	1107.4	1140.0	1117.6	999.2	875.7	788.9	712.4	644.0	565.4
47.5°	697.1	898.1	991.0	1043.1	1043.1	931.8	808.3	722.6	649.1	590.9	521.5
50°	601.1	768.5	864.4	932.8	951.2	863.4	747.1	663.4	594.0	530.7	477.6
52.5°	512.3	662.4	742.0	813.4	866.5	789.9	678.7	603.2	534.8	475.6	433.8
55°	442.9	555.2	627.7	706.3	765.5	715.4	612.4	538.9	479.7	430.7	395.0
57.5°	376.6	474.6	533.8	603.2	666.5	628.7	546.0	482.7	430.7	387.8	356.2
60°	320.5	400.1	446.0	500.1	578.7	552.1	483.8	425.6	383.7	345.0	318.4
62.5°	272.5	335.8	374.6	413.3	484.8	472.5	419.5	374.6	338.8	306.2	283.7
65°	223.5	275.6	306.2	339.9	397.0	402.1	359.3	327.6	295.0	266.4	246.0
67.5°	180.6	221.5	249.0	277.6	323.5	337.8	308.2	281.7	254.1	230.7	212.3
70°	145.9	174.5	194.9	217.4	255.2	272.5	257.2	238.8	216.4	197.0	180.6
72.5°	115.3	133.7	145.9	163.3	193.9	211.3	210.2	193.9	177.6	164.3	151.0
75°	84.7	99.0	109.2	120.4	144.9	161.3	165.3	158.2	141.9	131.7	121.5
77.5°	64.3	72.5	77.6	85.7	103.1	117.4	123.5	121.5	110.2	102.1	94.9
80°	49.0	51.0	53.1	56.1	70.4	83.7	87.8	86.8	80.6	77.6	69.4
82.5°	34.7	35.7	36.7	37.8	42.9	54.1	58.2	60.2	55.1	52.1	44.9
85°	20.4	21.4	21.4	23.5	24.5	27.6	34.7	34.7	33.7	29.6	28.6
87.5°	10.2	10.2	9.2	9.2	10.2	11.2	13.3	15.3	13.3	12.2	11.2
90°	7.1	5.3	4.8	4.2	3.5	2.8	1.4	0.4	1.4	2.8	3.5
92.5°	28.3	18.7	16.8	14.8	12.0	10.2	7.4	5.3	7.4	10.2	12.0
95°	50.9	34.6	30.4	26.2	20.5	17.3	13.8	12.4	13.8	17.3	20.5
97.5°	65.7	44.9	40.1	35.3	29.0	24.4	20.5	18.4	20.5	24.4	29.0
100°	72.8	54.1	49.2	44.2	37.1	31.5	28.3	27.2	28.3	31.5	37.1
102.5°	79.2	62.2	57.2	52.3	44.9	39.2	36.0	35.3	36.0	39.2	44.9
105°	86.6	70.0	65.0	60.1	52.3	47.0	44.5	43.1	44.5	47.0	52.3
107.5°	94.0	77.8	72.8	67.9	60.1	55.1	52.7	51.6	52.7	55.1	60.1
110°	101.4	85.9	80.8	75.6	68.2	63.6	61.5	60.1	61.5	63.6	68.2

TEST NUMBER: P1010146

CATALOG NUMBER: S122RDIP-B675D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	108.5	93.7	88.4	83.1	76.0	71.7	69.3	67.9	69.3	71.7	76.0
115°	115.9	100.7	96.0	91.2	84.1	79.9	77.8	76.0	77.8	79.9	84.1
117.5°	122.6	108.5	103.6	98.6	91.9	88.0	85.9	84.5	85.9	88.0	91.9
120°	129.7	115.9	111.0	106.0	99.0	95.8	93.7	92.2	93.7	95.8	99.0
122.5°	136.4	123.7	118.6	113.4	106.4	102.8	100.7	99.7	100.7	102.8	106.4
125°	143.1	130.4	125.4	120.5	113.4	109.2	107.1	106.0	107.1	109.2	113.4
127.5°	149.5	137.1	132.0	126.9	120.2	115.6	112.7	111.3	112.7	115.6	120.2
130°	155.1	142.8	137.9	132.9	125.8	120.9	117.3	115.9	117.3	120.9	125.8
132.5°	160.1	148.4	143.4	138.5	131.1	125.8	121.9	120.2	121.9	125.8	131.1
135°	164.7	153.4	148.4	143.5	135.4	130.1	125.8	124.4	125.8	130.1	135.4
137.5°	168.6	157.3	152.7	148.1	140.0	134.3	130.1	128.3	130.1	134.3	140.0
140°	171.8	161.2	156.6	152.0	144.2	138.5	134.3	132.9	134.3	138.5	144.2
142.5°	174.2	164.0	159.8	155.5	148.1	142.4	138.5	137.5	138.5	142.4	148.1
145°	176.7	167.2	163.3	159.4	152.3	147.0	143.5	142.1	143.5	147.0	152.3
147.5°	178.8	169.6	166.1	162.6	156.6	151.6	148.1	147.0	148.1	151.6	156.6
150°	180.2	172.1	169.0	165.8	160.5	155.9	153.0	152.0	153.0	155.9	160.5
152.5°	181.7	174.6	171.8	168.9	164.0	160.1	157.3	156.9	157.3	160.1	164.0
155°	183.1	177.1	174.4	171.8	167.9	164.0	161.9	161.5	161.9	164.0	167.9
157.5°	184.1	178.8	176.5	174.2	171.1	167.5	165.8	165.4	165.8	167.5	171.1
160°	184.8	180.6	178.6	176.7	173.9	171.1	169.6	169.3	169.6	171.1	173.9
162.5°	185.2	181.7	180.2	178.8	176.4	174.2	172.8	173.2	172.8	174.2	176.4
165°	185.5	182.4	181.3	180.2	178.5	176.4	175.6	176.0	175.6	176.4	178.5
167.5°	185.5	183.1	182.4	181.7	180.2	178.8	178.1	178.5	178.1	178.8	180.2
170°	185.2	183.4	182.9	182.4	181.7	180.6	180.2	180.9	180.2	180.6	181.7
172.5°	184.8	183.8	183.4	183.1	182.7	181.7	182.0	182.4	182.0	181.7	182.7
175°	184.5	183.8	183.6	183.4	183.4	182.7	183.1	183.4	183.1	182.7	183.4
177.5°	184.1	183.8	183.8	183.8	183.8	183.1	183.4	184.1	183.4	183.1	183.8
180°	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8

TEST NUMBER: P1010146

CATALOG NUMBER: S122RDIP-B675D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6
2.5°	1452.3	1453.3	1456.4	1447.2	1432.9	1426.8	1408.4	1405.4	1402.3	1402.3	1405.4
5°	1419.7	1415.6	1416.6	1399.2	1378.8	1366.6	1341.1	1345.2	1331.9	1323.7	1325.8
7.5°	1383.9	1372.7	1371.7	1349.2	1323.7	1301.3	1274.7	1268.6	1256.4	1242.1	1235.9
10°	1339.0	1330.9	1315.6	1290.0	1257.4	1239.0	1203.3	1181.9	1178.8	1157.4	1149.2
12.5°	1293.1	1278.8	1263.5	1227.8	1191.0	1161.4	1134.9	1111.4	1095.1	1076.7	1064.5
15°	1240.0	1222.7	1205.3	1167.6	1124.7	1095.1	1055.3	1020.6	972.6	934.9	913.4
17.5°	1181.9	1162.5	1139.0	1097.1	1055.3	1014.5	941.0	900.2	866.5	844.0	830.8
20°	1121.6	1100.2	1076.7	1034.9	962.4	891.0	850.2	818.5	798.1	775.7	759.3
22.5°	1058.4	1035.9	1010.4	945.1	868.5	818.5	786.9	757.3	727.7	715.4	707.3
25°	999.2	978.8	946.1	857.3	797.1	751.2	715.4	696.0	680.7	664.4	649.1
27.5°	937.9	900.2	854.2	779.7	742.0	695.0	669.5	655.2	628.7	617.5	610.3
30°	864.4	822.6	778.7	725.6	681.8	649.1	625.6	602.2	586.8	575.6	563.4
32.5°	789.9	750.1	722.6	667.5	634.8	601.1	578.7	564.4	541.9	534.8	529.7
35°	725.6	692.0	667.5	622.6	591.9	561.3	545.0	523.6	509.3	496.0	487.8
37.5°	662.4	644.0	618.5	580.7	548.1	523.6	501.1	494.0	474.6	467.4	459.3
40°	618.5	590.9	569.5	536.8	509.3	482.7	468.5	452.1	438.9	427.6	424.6
42.5°	565.4	545.0	532.8	497.0	468.5	453.1	435.8	417.4	407.2	398.0	386.8
45°	525.6	507.2	489.9	461.3	435.8	416.4	401.1	388.8	371.5	367.4	350.1
47.5°	483.8	465.4	452.1	423.5	400.1	381.7	370.5	354.1	339.9	330.7	322.5
50°	441.9	426.6	414.4	389.9	369.5	350.1	334.8	318.4	312.3	297.0	291.9
52.5°	402.1	391.9	378.6	355.2	334.8	318.4	302.1	288.8	279.6	271.5	265.4
55°	368.4	352.1	346.0	320.5	303.1	285.8	271.5	263.3	252.1	247.0	241.9
57.5°	330.7	321.5	311.3	291.9	272.5	256.2	246.0	233.7	227.6	221.5	217.4
60°	298.0	284.7	276.6	260.3	242.9	227.6	218.4	209.2	201.1	196.0	187.8
62.5°	260.3	250.0	244.9	227.6	213.3	199.0	190.9	181.7	175.5	166.4	156.2
65°	227.6	219.4	213.3	199.0	185.7	172.5	164.3	153.1	144.9	139.8	138.8
67.5°	199.0	192.9	183.7	170.4	157.2	147.0	137.8	128.6	127.6	125.5	125.5
70°	167.4	161.3	156.2	141.9	130.6	119.4	117.4	114.3	111.2	110.2	108.2
72.5°	139.8	134.7	128.6	116.3	105.1	102.1	100.0	98.0	94.9	93.9	92.9
75°	113.3	106.1	102.1	90.8	87.8	85.7	83.7	80.6	78.6	77.6	75.5
77.5°	86.8	79.6	79.6	73.5	71.4	68.4	66.3	64.3	63.3	61.2	61.2
80°	61.2	61.2	59.2	56.1	53.1	52.1	49.0	48.0	46.9	48.0	45.9
82.5°	44.9	40.8	40.8	38.8	36.7	35.7	33.7	33.7	32.7	32.7	32.7
85°	25.5	25.5	24.5	22.5	21.4	21.4	20.4	20.4	19.4	19.4	18.4
87.5°	10.2	9.2	10.2	9.2	9.2	8.2	8.2	8.2	7.1	8.2	7.1
90°	4.2	4.8	5.3	7.1	9.5	11.7	12.0	11.7	11.3	10.6	11.3
92.5°	14.8	16.8	18.7	28.3	41.7	53.7	54.4	45.6	35.7	30.4	26.5
95°	26.2	30.4	34.6	50.9	81.6	122.6	138.5	121.2	92.6	71.0	56.2
97.5°	35.3	40.1	44.9	65.7	108.5	174.6	225.8	227.6	189.4	151.3	115.6
100°	44.2	49.2	54.1	72.8	115.9	192.3	279.2	330.1	322.7	278.8	230.4
102.5°	52.3	57.2	62.2	79.2	116.3	185.5	281.0	368.3	410.0	408.5	376.4
105°	60.1	65.0	70.0	86.6	118.0	176.4	261.9	355.9	429.4	469.3	473.9
107.5°	67.9	72.8	77.8	94.0	121.9	171.4	244.2	329.7	408.5	467.9	502.6
110°	75.6	80.8	85.9	101.4	126.9	170.0	232.2	305.4	379.9	443.2	488.4

TEST NUMBER: P1010146

CATALOG NUMBER: S122RDIP-B675D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	83.1	88.4	93.7	108.5	132.2	170.3	224.4	288.4	353.8	413.8	463.0
115°	91.2	96.0	100.7	115.9	137.5	171.8	219.1	275.0	333.3	387.7	434.0
117.5°	98.6	103.6	108.5	122.6	143.1	173.9	216.3	265.8	316.3	365.1	408.2
120°	106.0	111.0	115.9	129.7	148.8	176.0	213.8	258.7	304.3	348.1	385.6
122.5°	113.4	118.6	123.7	136.4	153.7	178.5	212.4	252.7	294.7	334.0	369.0
125°	120.5	125.4	130.4	143.1	159.0	180.9	210.6	247.0	285.6	322.0	353.1
127.5°	126.9	132.0	137.1	149.5	164.0	183.4	209.6	241.7	276.4	309.9	339.6
130°	132.9	137.9	142.8	155.1	168.6	186.2	208.9	236.4	267.5	297.9	325.8
132.5°	138.5	143.4	148.4	160.1	173.2	189.1	208.5	232.2	259.1	286.6	311.7
135°	143.5	148.4	153.4	164.7	177.1	191.2	208.2	228.3	251.3	274.6	297.9
137.5°	148.1	152.7	157.3	168.6	180.2	193.3	208.2	225.5	244.9	265.1	284.1
140°	152.0	156.6	161.2	171.8	182.7	194.7	207.8	223.0	238.9	255.9	272.1
142.5°	155.5	159.8	164.0	174.2	184.8	195.8	207.8	220.5	234.0	247.7	261.2
145°	159.4	163.3	167.2	176.7	186.6	196.5	207.1	218.4	229.4	241.0	252.0
147.5°	162.6	166.1	169.6	178.8	187.7	196.9	206.0	216.3	225.8	235.4	244.2
150°	165.8	169.0	172.1	180.2	188.4	196.5	205.0	213.5	221.9	229.7	237.1
152.5°	168.9	171.8	174.6	181.7	188.7	195.8	203.2	211.0	218.1	225.1	231.1
155°	171.8	174.4	177.1	183.1	189.1	195.1	201.1	207.8	214.5	220.2	225.5
157.5°	174.2	176.5	178.8	184.1	189.1	193.7	199.0	205.0	210.3	215.2	219.8
160°	176.7	178.6	180.6	184.8	189.1	192.6	196.9	201.8	206.4	210.3	214.2
162.5°	178.8	180.2	181.7	185.2	188.7	191.6	195.1	199.0	202.5	205.7	208.9
165°	180.2	181.3	182.4	185.5	188.0	190.1	192.6	195.8	198.6	201.1	203.6
167.5°	181.7	182.4	183.1	185.5	187.7	188.7	190.5	192.6	194.7	196.9	198.6
170°	182.4	182.9	183.4	185.2	187.0	187.7	188.7	190.1	191.9	193.0	194.4
172.5°	183.1	183.4	183.8	184.8	185.9	186.2	186.6	187.7	188.7	189.4	190.5
175°	183.4	183.6	183.8	184.5	185.2	184.8	185.2	185.5	186.6	187.0	187.3
177.5°	183.8	183.8	183.8	184.1	184.8	184.1	183.8	184.1	184.8	184.8	185.2
180°	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8

TEST NUMBER: P1010146

CATALOG NUMBER: S122RDIP-B675D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6
2.5°	1405.4	1403.3	1397.2	1399.2	1396.2	1396.2	1394.1	1394.1	1394.1	1399.2	1396.2
5°	1328.8	1321.7	1314.5	1311.5	1308.4	1305.3	1305.3	1304.3	1313.5	1311.5	1319.6
7.5°	1233.9	1231.9	1217.6	1217.6	1212.5	1210.4	1215.5	1216.6	1217.6	1219.6	1224.7
10°	1149.2	1144.1	1123.7	1125.7	1122.7	1118.6	1121.6	1119.6	1126.7	1128.8	1126.7
12.5°	1049.2	1040.0	1017.5	1006.3	994.1	984.9	996.1	987.9	1016.5	1024.7	1047.1
15°	916.5	899.1	883.8	883.8	872.6	864.4	869.6	878.7	884.9	894.0	898.1
17.5°	827.7	820.6	808.3	801.2	798.1	795.0	795.0	799.1	812.4	811.4	819.5
20°	752.2	748.1	742.0	732.8	729.7	727.7	727.7	727.7	736.9	745.0	750.1
22.5°	700.1	697.1	693.0	680.7	674.6	672.6	677.7	680.7	687.9	694.0	699.1
25°	648.1	640.9	633.8	629.7	626.6	626.6	628.7	629.7	632.8	635.8	642.0
27.5°	605.2	600.1	589.9	578.7	578.7	575.6	577.7	579.7	586.8	597.1	602.2
30°	557.2	556.2	552.1	548.1	544.0	541.9	546.0	549.1	550.1	555.2	555.2
32.5°	522.5	515.4	508.3	504.2	502.1	501.1	502.1	506.2	506.2	512.3	519.5
35°	487.8	483.8	476.6	469.5	467.4	462.3	466.4	470.5	477.6	480.7	483.8
37.5°	450.1	445.0	441.9	439.9	435.8	436.8	433.8	439.9	446.0	445.0	447.0
40°	421.5	412.3	403.1	402.1	401.1	400.1	400.1	401.1	405.2	409.3	415.4
42.5°	384.8	381.7	373.5	365.4	363.3	361.3	359.3	363.3	371.5	378.6	381.7
45°	347.0	342.9	340.9	334.8	330.7	329.7	327.6	332.7	339.9	342.9	345.0
47.5°	312.3	311.3	305.2	306.2	303.1	304.1	303.1	306.2	306.2	309.2	311.3
50°	288.8	285.8	282.7	280.7	277.6	277.6	276.6	277.6	281.7	285.8	284.7
52.5°	265.4	260.3	259.2	258.2	256.2	258.2	255.2	256.2	260.3	262.3	261.3
55°	237.8	236.8	234.7	232.7	231.7	230.7	230.7	230.7	234.7	237.8	238.8
57.5°	216.4	211.3	207.2	207.2	203.1	202.1	204.1	205.1	208.2	210.2	212.3
60°	186.8	184.7	178.6	175.5	169.4	168.4	168.4	172.5	177.6	184.7	186.8
62.5°	155.1	152.1	151.0	151.0	151.0	151.0	151.0	151.0	151.0	152.1	152.1
65°	137.8	138.8	137.8	136.8	137.8	137.8	136.8	136.8	136.8	137.8	138.8
67.5°	123.5	122.5	123.5	122.5	121.5	121.5	120.4	121.5	122.5	123.5	123.5
70°	107.2	107.2	106.1	107.2	106.1	105.1	104.1	104.1	106.1	107.2	107.2
72.5°	91.9	91.9	90.8	90.8	88.8	88.8	89.8	88.8	88.8	91.9	91.9
75°	76.5	75.5	74.5	74.5	73.5	73.5	73.5	72.5	74.5	74.5	75.5
77.5°	60.2	60.2	60.2	59.2	59.2	58.2	58.2	59.2	59.2	59.2	60.2
80°	45.9	45.9	45.9	44.9	43.9	43.9	43.9	43.9	43.9	44.9	43.9
82.5°	31.6	31.6	31.6	31.6	31.6	30.6	30.6	30.6	31.6	31.6	30.6
85°	19.4	18.4	19.4	19.4	18.4	19.4	18.4	18.4	17.4	17.4	18.4
87.5°	8.2	7.1	6.1	6.1	7.1	6.1	6.1	6.1	7.1	6.1	6.1
90°	11.5	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.5
92.5°	25.1	23.7	23.3	21.9	22.3	21.6	22.3	21.9	23.3	23.7	25.1
95°	52.3	48.4	43.8	41.0	39.9	40.3	39.9	41.0	43.8	48.4	52.3
97.5°	105.0	94.4	80.6	73.5	69.6	67.5	69.6	73.5	80.6	94.4	105.0
100°	209.0	187.7	158.3	143.1	132.9	126.5	132.9	143.1	158.3	187.7	209.0
102.5°	353.4	330.4	297.9	269.3	255.9	246.7	255.9	269.3	297.9	330.4	353.4
105°	468.1	462.3	440.4	418.4	403.2	398.3	403.2	418.4	440.4	462.3	468.1
107.5°	509.6	516.7	516.3	513.2	508.6	500.4	508.6	513.2	516.3	516.7	509.6
110°	502.9	517.4	532.6	539.3	542.5	542.1	542.5	539.3	532.6	517.4	502.9

TEST NUMBER: P1010146

CATALOG NUMBER: S122RDIP-B675D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	480.2	497.3	519.9	532.2	539.0	541.4	539.0	532.2	519.9	497.3	480.2
115°	452.2	470.4	495.5	511.7	520.9	524.1	520.9	511.7	495.5	470.4	452.2
117.5°	425.5	442.8	468.6	485.9	495.5	498.0	495.5	485.9	468.6	442.8	425.5
120°	401.6	417.7	442.5	459.1	469.3	472.9	469.3	459.1	442.5	417.7	401.6
122.5°	383.1	397.2	418.8	435.1	443.9	446.7	443.9	435.1	418.8	397.2	383.1
125°	366.4	379.6	400.1	413.5	422.3	425.2	422.3	413.5	400.1	379.6	366.4
127.5°	352.0	364.4	382.4	395.1	402.9	405.0	402.9	395.1	382.4	364.4	352.0
130°	337.5	349.2	366.5	378.5	385.6	388.4	385.6	378.5	366.5	349.2	337.5
132.5°	322.5	333.3	350.2	362.3	368.6	371.1	368.6	362.3	350.2	333.3	322.5
135°	307.8	317.7	332.9	344.6	350.9	352.4	350.9	344.6	332.9	317.7	307.8
137.5°	293.0	301.8	316.3	326.6	332.2	334.3	332.2	326.6	316.3	301.8	293.0
140°	279.9	287.7	299.0	308.2	313.5	315.6	313.5	308.2	299.0	287.7	279.9
142.5°	267.4	273.5	284.1	292.3	296.9	296.9	296.9	292.3	284.1	273.5	267.4
145°	257.1	262.2	270.7	276.7	280.3	281.3	280.3	276.7	270.7	262.2	257.1
147.5°	248.1	252.0	259.4	264.4	266.8	267.5	266.8	264.4	259.4	252.0	248.1
150°	240.3	243.5	248.8	253.0	255.2	255.5	255.2	253.0	248.8	243.5	240.3
152.5°	233.8	236.4	240.3	243.9	245.3	245.3	245.3	243.9	240.3	236.4	233.8
155°	227.4	229.4	233.3	235.7	237.1	236.4	237.1	235.7	233.3	229.4	227.4
157.5°	221.4	223.0	225.8	228.0	228.7	228.7	228.7	228.0	225.8	223.0	221.4
160°	215.4	216.6	219.1	220.9	221.2	221.2	221.2	220.9	219.1	216.6	215.4
162.5°	209.8	210.6	213.1	214.2	214.5	214.2	214.5	214.2	213.1	210.6	209.8
165°	204.3	205.0	206.4	207.8	207.8	207.5	207.8	207.8	206.4	205.0	204.3
167.5°	199.3	200.0	200.7	201.4	201.4	201.1	201.4	201.4	200.7	200.0	199.3
170°	194.8	195.1	195.4	196.5	196.1	195.4	196.1	196.5	195.4	195.1	194.8
172.5°	190.6	190.8	191.2	191.6	191.2	190.8	191.2	191.6	191.2	190.8	190.6
175°	187.5	187.7	187.7	188.0	187.7	187.0	187.7	188.0	187.7	187.7	187.5
177.5°	185.2	185.2	185.2	185.2	184.8	184.1	184.8	185.2	185.2	185.2	185.2
180°	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8

TEST NUMBER: P1010146

CATALOG NUMBER: S122RDIP-B675D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6
2.5°	1399.2	1404.3	1402.3	1391.1	1402.3	1405.4	1411.5	1417.6	1421.7	1427.8	1432.9
5°	1311.5	1321.7	1327.8	1321.7	1342.1	1345.2	1359.4	1367.6	1379.9	1390.1	1398.2
7.5°	1228.8	1237.0	1249.2	1251.3	1263.5	1277.8	1298.2	1318.6	1338.0	1348.2	1357.4
10°	1140.0	1154.3	1172.7	1168.6	1187.0	1209.4	1230.8	1263.5	1279.8	1298.2	1314.5
12.5°	1051.2	1060.4	1084.9	1093.1	1119.6	1136.9	1166.5	1187.0	1227.8	1249.2	1263.5
15°	896.1	933.8	964.5	1001.2	1035.9	1068.6	1095.1	1131.8	1167.6	1183.9	1207.4
17.5°	825.7	843.0	861.4	879.8	924.7	982.8	1029.8	1069.6	1100.2	1121.6	1149.2
20°	752.2	769.5	789.9	807.3	834.9	876.7	934.9	1003.3	1040.0	1062.4	1089.0
22.5°	700.1	716.5	729.7	745.0	766.5	797.1	841.0	925.7	974.7	1002.2	1025.7
25°	644.0	664.4	678.7	689.9	707.3	741.0	776.7	824.6	912.4	933.8	966.5
27.5°	605.2	611.3	627.7	645.0	662.4	680.7	717.5	758.3	817.5	864.4	904.3
30°	559.3	574.6	589.9	597.1	612.4	638.9	661.3	705.2	751.2	787.9	835.9
32.5°	524.6	533.8	544.0	561.3	575.6	594.0	616.4	653.2	692.0	715.4	752.2
35°	485.8	491.9	513.4	520.5	534.8	553.2	575.6	604.2	646.0	664.4	690.9
37.5°	449.1	463.4	469.5	485.8	499.1	517.4	533.8	566.4	594.0	615.4	639.9
40°	420.5	426.6	437.8	452.1	463.4	477.6	498.1	521.5	551.1	568.5	589.9
42.5°	385.8	390.9	405.2	413.3	431.7	445.0	457.2	485.8	512.3	525.6	547.0
45°	348.0	360.3	369.5	385.8	396.0	412.3	427.6	448.0	472.5	487.8	500.1
47.5°	315.4	327.6	336.8	352.1	368.4	375.6	391.9	413.3	435.8	448.0	465.4
50°	288.8	292.9	310.3	317.4	334.8	349.0	360.3	378.6	403.1	410.3	424.6
52.5°	263.3	266.4	277.6	286.8	302.1	314.3	328.6	346.0	366.4	377.6	388.8
55°	240.9	242.9	248.0	258.2	268.4	283.7	297.0	313.3	330.7	342.9	353.1
57.5°	215.3	219.4	223.5	229.6	239.8	254.1	268.4	283.7	298.0	306.2	319.4
60°	185.7	191.9	199.0	206.2	213.3	223.5	239.8	254.1	267.4	274.5	284.7
62.5°	154.1	166.4	172.5	180.6	186.8	196.0	208.2	224.5	233.7	242.9	251.1
65°	138.8	139.8	140.8	149.0	160.2	169.4	180.6	192.9	207.2	213.3	219.4
67.5°	123.5	124.5	126.6	127.6	131.7	141.9	154.1	167.4	178.6	182.7	188.8
70°	108.2	108.2	112.3	113.3	114.3	115.3	125.5	138.8	149.0	154.1	161.3
72.5°	91.9	92.9	94.9	95.9	98.0	100.0	103.1	110.2	122.5	127.6	135.7
75°	75.5	76.5	77.6	78.6	81.6	82.7	85.7	89.8	94.9	101.0	106.1
77.5°	60.2	60.2	61.2	63.3	65.3	66.3	69.4	71.4	73.5	76.5	80.6
80°	44.9	45.9	45.9	48.0	48.0	49.0	50.0	53.1	55.1	57.2	59.2
82.5°	30.6	32.7	32.7	32.7	33.7	34.7	35.7	35.7	37.8	38.8	41.8
85°	18.4	19.4	19.4	19.4	18.4	20.4	20.4	21.4	21.4	21.4	22.5
87.5°	7.1	6.1	7.1	7.1	7.1	8.2	7.1	7.1	8.2	9.2	9.2
90°	11.3	10.6	11.3	11.7	12.0	11.7	9.5	7.1	5.3	4.8	4.2
92.5°	26.5	30.4	35.7	45.6	54.4	53.7	41.7	28.3	18.7	16.8	14.8
95°	56.2	71.0	92.6	121.2	138.5	122.6	81.6	50.9	34.6	30.4	26.2
97.5°	115.6	151.3	189.4	227.6	225.8	174.6	108.5	65.7	44.9	40.1	35.3
100°	230.4	278.8	322.7	330.1	279.2	192.3	115.9	72.8	54.1	49.2	44.2
102.5°	376.4	408.5	410.0	368.3	281.0	185.5	116.3	79.2	62.2	57.2	52.3
105°	473.9	469.3	429.4	355.9	261.9	176.4	118.0	86.6	70.0	65.0	60.1
107.5°	502.6	467.9	408.5	329.7	244.2	171.4	121.9	94.0	77.8	72.8	67.9
110°	488.4	443.2	379.9	305.4	232.2	170.0	126.9	101.4	85.9	80.8	75.6

TEST NUMBER: P1010146

CATALOG NUMBER: S122RDIP-B675D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	463.0	413.8	353.8	288.4	224.4	170.3	132.2	108.5	93.7	88.4	83.1
115°	434.0	387.7	333.3	275.0	219.1	171.8	137.5	115.9	100.7	96.0	91.2
117.5°	408.2	365.1	316.3	265.8	216.3	173.9	143.1	122.6	108.5	103.6	98.6
120°	385.6	348.1	304.3	258.7	213.8	176.0	148.8	129.7	115.9	111.0	106.0
122.5°	369.0	334.0	294.7	252.7	212.4	178.5	153.7	136.4	123.7	118.6	113.4
125°	353.1	322.0	285.6	247.0	210.6	180.9	159.0	143.1	130.4	125.4	120.5
127.5°	339.6	309.9	276.4	241.7	209.6	183.4	164.0	149.5	137.1	132.0	126.9
130°	325.8	297.9	267.5	236.4	208.9	186.2	168.6	155.1	142.8	137.9	132.9
132.5°	311.7	286.6	259.1	232.2	208.5	189.1	173.2	160.1	148.4	143.4	138.5
135°	297.9	274.6	251.3	228.3	208.2	191.2	177.1	164.7	153.4	148.4	143.5
137.5°	284.1	265.1	244.9	225.5	208.2	193.3	180.2	168.6	157.3	152.7	148.1
140°	272.1	255.9	238.9	223.0	207.8	194.7	182.7	171.8	161.2	156.6	152.0
142.5°	261.2	247.7	234.0	220.5	207.8	195.8	184.8	174.2	164.0	159.8	155.5
145°	252.0	241.0	229.4	218.4	207.1	196.5	186.6	176.7	167.2	163.3	159.4
147.5°	244.2	235.4	225.8	216.3	206.0	196.9	187.7	178.8	169.6	166.1	162.6
150°	237.1	229.7	221.9	213.5	205.0	196.5	188.4	180.2	172.1	169.0	165.8
152.5°	231.1	225.1	218.1	211.0	203.2	195.8	188.7	181.7	174.6	171.8	168.9
155°	225.5	220.2	214.5	207.8	201.1	195.1	189.1	183.1	177.1	174.4	171.8
157.5°	219.8	215.2	210.3	205.0	199.0	193.7	189.1	184.1	178.8	176.5	174.2
160°	214.2	210.3	206.4	201.8	196.9	192.6	189.1	184.8	180.6	178.6	176.7
162.5°	208.9	205.7	202.5	199.0	195.1	191.6	188.7	185.2	181.7	180.2	178.8
165°	203.6	201.1	198.6	195.8	192.6	190.1	188.0	185.5	182.4	181.3	180.2
167.5°	198.6	196.9	194.7	192.6	190.5	188.7	187.7	185.5	183.1	182.4	181.7
170°	194.4	193.0	191.9	190.1	188.7	187.7	187.0	185.2	183.4	182.9	182.4
172.5°	190.5	189.4	188.7	187.7	186.6	186.2	185.9	184.8	183.8	183.4	183.1
175°	187.3	187.0	186.6	185.5	185.2	184.8	185.2	184.5	183.8	183.6	183.4
177.5°	185.2	184.8	184.8	184.1	183.8	184.1	184.8	184.1	183.8	183.8	183.8
180°	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8

TEST NUMBER: P1010146

CATALOG NUMBER: S122RDIP-B675D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1468.6	1468.6	1468.6	1468.6
2.5°	1442.1	1439.0	1457.4	1477.8
5°	1412.5	1417.6	1441.1	1469.7
7.5°	1381.9	1393.1	1420.7	1458.4
10°	1339.0	1359.4	1401.3	1440.1
12.5°	1297.2	1324.7	1364.5	1410.5
15°	1250.2	1280.9	1329.8	1385.0
17.5°	1198.2	1232.9	1290.0	1350.3
20°	1143.1	1189.0	1249.2	1314.5
22.5°	1081.8	1136.9	1199.2	1271.7
25°	1022.6	1082.9	1145.1	1228.8
27.5°	964.5	1023.7	1093.1	1177.8
30°	906.3	960.4	1034.9	1125.7
32.5°	844.0	900.2	978.8	1071.6
35°	786.9	843.0	916.5	1008.4
37.5°	725.6	785.9	856.3	951.2
40°	654.2	724.6	793.0	883.8
42.5°	595.0	669.5	735.9	821.6
45°	548.1	618.5	673.6	757.3
47.5°	504.2	561.3	617.5	695.0
50°	462.3	506.2	564.4	633.8
52.5°	419.5	457.2	507.2	572.6
55°	380.7	416.4	461.3	511.3
57.5°	345.0	370.5	415.4	460.3
60°	305.2	331.7	366.4	404.2
62.5°	271.5	291.9	324.6	356.2
65°	235.8	255.2	279.6	309.2
67.5°	203.1	220.4	239.8	263.3
70°	173.5	186.8	201.1	221.5
72.5°	141.9	156.2	169.4	185.7
75°	116.3	122.5	133.7	144.9
77.5°	89.8	98.0	104.1	113.3
80°	64.3	71.4	73.5	80.6
82.5°	42.9	46.9	51.0	53.1
85°	24.5	26.5	30.6	31.6
87.5°	9.2	10.2	12.2	14.3
90°	3.5	2.8	1.4	0.4
92.5°	12.0	10.2	7.4	5.3
95°	20.5	17.3	13.8	12.4
97.5°	29.0	24.4	20.5	18.4
100°	37.1	31.5	28.3	27.2
102.5°	44.9	39.2	36.0	35.3
105°	52.3	47.0	44.5	43.1
107.5°	60.1	55.1	52.7	51.6
110°	68.2	63.6	61.5	60.1

TEST NUMBER: P1010146

CATALOG NUMBER: S122RDIP-B675D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	76.0	71.7	69.3	67.9
115°	84.1	79.9	77.8	76.0
117.5°	91.9	88.0	85.9	84.5
120°	99.0	95.8	93.7	92.2
122.5°	106.4	102.8	100.7	99.7
125°	113.4	109.2	107.1	106.0
127.5°	120.2	115.6	112.7	111.3
130°	125.8	120.9	117.3	115.9
132.5°	131.1	125.8	121.9	120.2
135°	135.4	130.1	125.8	124.4
137.5°	140.0	134.3	130.1	128.3
140°	144.2	138.5	134.3	132.9
142.5°	148.1	142.4	138.5	137.5
145°	152.3	147.0	143.5	142.1
147.5°	156.6	151.6	148.1	147.0
150°	160.5	155.9	153.0	152.0
152.5°	164.0	160.1	157.3	156.9
155°	167.9	164.0	161.9	161.5
157.5°	171.1	167.5	165.8	165.4
160°	173.9	171.1	169.6	169.3
162.5°	176.4	174.2	172.8	173.2
165°	178.5	176.4	175.6	176.0
167.5°	180.2	178.8	178.1	178.5
170°	181.7	180.6	180.2	180.9
172.5°	182.7	181.7	182.0	182.4
175°	183.4	182.7	183.1	183.4
177.5°	183.8	183.1	183.4	184.1
180°	183.8	183.8	183.8	183.8

(END OF REPORT)