

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010156

Luminaire Tested: S122RDIP-B675D530UB27-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010156
REPORT IS A COMBINATION OF REPORTS P988498 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B675D530UB27-4F0-XX-W2A-A
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4632.0 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010156

CATALOG NUMBER: S122RDIP-B675D530UB27-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1010156

CATALOG NUMBER: S122RDIP-B675D530UB27-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	100	96	92	89	92	89	86	83	77	74	72	65	64	62	55	54	53
2	91	85	79	74	85	79	74	70	68	65	61	58	56	53	49	47	46
3	84	75	68	63	78	70	64	59	61	56	53	52	49	46	44	42	40
4	77	67	60	54	72	63	56	51	55	50	46	47	44	41	40	38	35
5	72	60	53	47	66	57	50	45	50	44	40	43	39	36	37	34	31
6	66	55	47	41	62	51	45	40	45	40	36	39	35	32	34	31	28
7	62	50	42	37	57	47	40	35	41	36	32	36	32	29	31	28	26
8	57	46	38	33	53	43	36	32	38	33	29	33	29	26	29	26	23
9	54	42	35	30	50	40	33	29	35	30	26	31	27	24	27	24	21
10	50	39	32	27	47	37	30	26	33	27	24	29	25	22	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23174	23174	23174	23174
5°	23228	24614	23309	19664
10°	22972	26017	23135	16239
15°	22474	26025	22855	12199
20°	21875	21513	22351	10065
25°	21147	13443	21605	8562
30°	20220	8607	20769	7371
35°	19090	6615	19708	6308
40°	17833	5560	18594	5517
45°	16487	4732	17175	4632
50°	15109	4020	15814	4006
55°	13582	3495	14314	3448
60°	12226	2664	12872	2633
65°	10960	2006	11610	2274
70°	9562	1601	10311	1854
75°	8083	1227	8822	1403
80°	6419	835	6906	919
85°	4450	430	4887	454

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 21199 cd/sqm

TEST NUMBER: P1010156

CATALOG NUMBER: S122RDIP-B675D530UB27-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.9	3.0
10°-20°	387.6	8.4
20°-30°	498.8	10.8
30°-40°	473.3	10.2
40°-50°	405.6	8.8
50°-60°	308.9	6.7
60°-70°	194.8	4.2
70°-80°	97.2	2.1
80°-90°	26.2	0.6
90°-100°	23.6	0.5
100°-110°	88.1	1.9
110°-120°	233.6	5.0
120°-130°	387.5	8.4
130°-140°	411.6	8.9
140°-150°	382.5	8.3
150°-160°	307.5	6.6
160°-170°	198.2	4.3
170°-180°	68.2	1.5
0°-30°	1025.3	22.1
0°-40°	1498.6	32.4
0°-60°	2213.0	47.8
0°-90°	2531.3	54.6
90°-120°	345.3	7.5
90°-150°	1526.9	33.0
90°-180°	2101.0	45.4
0°-180°	4632.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1464	1464	1464	1464	1464	
5°	1465	1629	1470	1301	1465	139
15°	1381	1838	1404	862	1381	388
25°	1225	981	1251	625	1225	562
35°	1005	483	1038	461	1005	629
45°	755	336	786	329	755	583
55°	510	233	537	230	510	459
65°	308	121	327	137	308	306
75°	144	64	158	73	144	156
85°	32	18	35	19	32	36
90°	0	14	0	14	0	4
95°	34	22	34	22	34	40
105°	158	39	158	39	158	168
115°	298	42	298	42	298	293
125°	422	443	422	443	422	376
135°	522	539	522	539	522	403
145°	605	614	605	614	605	378
155°	666	667	666	667	666	307
165°	702	700	702	700	702	198
175°	718	714	718	714	718	68
180°	717	717	717	717	717	

TEST NUMBER: P1010156

CATALOG NUMBER: S122RDIP-B675D530UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1473.2	1479.3	1482.3	1486.4	1495.6	1501.7	1510.8	1512.8	1511.8	1515.9	1504.7
5°	1465.0	1478.3	1490.5	1500.6	1516.9	1527.1	1538.3	1551.5	1554.6	1569.8	1560.7
7.5°	1453.8	1473.2	1490.5	1510.8	1535.2	1548.5	1565.8	1586.1	1595.3	1613.6	1618.7
10°	1435.5	1463.0	1492.5	1513.9	1547.4	1570.8	1587.1	1619.7	1641.0	1668.5	1664.4
12.5°	1406.0	1441.6	1481.3	1516.9	1560.7	1575.9	1606.4	1640.0	1667.5	1692.9	1715.3
15°	1380.6	1421.3	1465.0	1508.8	1558.6	1587.1	1617.6	1661.4	1690.9	1735.7	1755.0
17.5°	1346.0	1397.9	1449.8	1498.6	1557.6	1590.2	1627.8	1670.5	1714.3	1757.0	1772.3
20°	1310.4	1366.3	1422.3	1488.4	1555.6	1587.1	1625.8	1678.7	1721.4	1755.0	1755.0
22.5°	1267.7	1335.8	1399.9	1463.0	1536.2	1582.0	1621.7	1683.8	1714.3	1721.4	1693.9
25°	1224.9	1293.1	1363.3	1441.6	1525.1	1565.8	1610.5	1668.5	1678.7	1650.2	1579.0
27.5°	1174.1	1250.4	1329.7	1414.2	1501.7	1552.5	1593.2	1631.9	1612.6	1536.2	1425.4
30°	1122.2	1204.6	1294.1	1374.5	1480.3	1527.1	1561.7	1572.9	1511.8	1387.7	1244.3
32.5°	1068.3	1148.6	1243.2	1339.9	1446.7	1491.5	1513.9	1484.4	1372.5	1215.8	1040.8
35°	1005.2	1095.7	1194.4	1295.1	1400.9	1434.5	1447.7	1375.5	1232.1	1029.6	855.6
37.5°	948.2	1038.7	1144.6	1247.3	1350.1	1368.4	1355.2	1242.2	1060.1	859.7	689.8
40°	881.1	977.7	1081.5	1196.4	1280.9	1286.0	1253.4	1106.9	881.1	692.8	588.0
42.5°	819.0	916.7	1020.4	1137.4	1201.5	1184.2	1140.5	948.2	735.6	597.2	512.8
45°	754.9	847.5	959.4	1063.2	1108.9	1068.3	1002.1	797.6	617.6	513.8	448.7
47.5°	692.8	779.3	890.2	989.9	998.1	952.3	873.9	668.4	535.1	451.7	398.8
50°	631.8	718.3	822.0	904.5	896.3	833.2	744.7	580.9	464.9	398.8	355.1
52.5°	570.8	649.1	749.8	814.9	780.3	719.3	631.8	492.4	405.9	347.9	314.4
55°	509.7	583.0	669.4	723.4	668.4	598.2	536.2	422.2	352.0	305.2	279.8
57.5°	458.8	516.8	596.2	628.7	562.6	507.7	453.8	363.2	305.2	271.6	242.1
60°	402.9	455.8	520.9	540.2	472.1	427.3	381.5	307.2	261.5	232.0	212.6
62.5°	355.1	398.8	448.7	448.7	388.6	355.1	320.5	257.4	219.8	196.4	187.2
65°	308.3	339.8	375.4	371.3	320.5	291.0	263.5	212.6	184.1	167.9	158.7
67.5°	262.5	286.9	310.3	296.1	259.4	234.0	208.6	171.9	152.6	141.4	129.2
70°	220.8	240.1	252.3	239.1	202.5	181.1	162.8	138.4	123.1	108.9	101.7
72.5°	185.2	193.3	197.4	181.1	150.6	138.4	125.1	107.8	94.6	87.5	85.5
75°	144.5	151.6	148.5	136.3	110.9	101.7	91.6	79.4	76.3	72.2	70.2
77.5°	112.9	112.9	107.8	96.7	79.4	72.2	68.2	62.1	59.0	58.0	56.0
80°	80.4	79.4	76.3	64.1	53.9	49.9	49.9	45.8	44.8	42.7	42.7
82.5°	52.9	52.9	48.8	38.7	35.6	34.6	33.6	31.5	31.5	30.5	30.5
85°	31.5	29.5	24.4	21.4	20.3	20.3	19.3	18.3	19.3	18.3	18.3
87.5°	14.2	11.2	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
90°	0.5	1.8	3.0	4.3	5.6	6.2	6.7	7.6	8.5	9.5	10.4
92.5°	13.0	12.5	12.1	11.6	11.1	10.9	11.1	11.4	11.7	12.1	12.4
95°	33.7	29.9	26.1	22.3	18.5	16.6	17.0	17.8	18.6	19.4	20.2
97.5°	60.7	51.2	41.8	32.3	22.8	18.1	19.0	20.9	22.7	24.6	26.4
100°	91.8	76.0	60.2	44.4	28.6	20.7	21.7	23.7	25.6	27.6	29.6
102.5°	126.0	125.8	125.6	125.3	125.1	125.0	114.5	93.5	72.6	51.6	30.6
105°	157.6	161.1	164.5	168.0	171.5	173.2	157.5	126.0	94.5	63.1	31.6
107.5°	194.4	197.3	200.2	203.1	206.0	207.4	188.0	149.2	110.3	71.5	32.7
110°	229.7	232.1	234.5	237.0	239.4	240.6	223.9	190.6	157.3	124.0	90.7

TEST NUMBER: P1010156

CATALOG NUMBER: S122RDIP-B675D530UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	262.9	265.0	267.0	269.1	271.2	272.2	271.2	269.3	267.3	265.4	263.4
115°	298.1	300.1	302.1	304.0	306.0	307.0	308.4	311.3	314.2	317.0	319.9
117.5°	328.7	331.0	333.3	335.6	337.9	339.1	340.1	342.0	344.0	345.9	347.9
120°	363.0	364.7	366.4	368.1	369.8	370.7	371.7	373.8	375.9	378.0	380.1
122.5°	392.0	393.8	395.7	397.5	399.4	400.3	401.5	403.8	406.1	408.4	410.7
125°	421.5	423.0	424.5	426.0	427.5	428.3	429.4	431.6	433.7	435.9	438.1
127.5°	448.5	450.1	451.7	453.4	455.0	455.8	456.7	458.4	460.1	461.8	463.5
130°	473.9	475.7	477.6	479.4	481.3	482.2	482.8	484.1	485.4	486.6	487.9
132.5°	499.8	501.3	502.8	504.3	505.8	506.6	507.2	508.5	509.8	511.0	512.3
135°	521.6	523.4	525.3	527.1	529.0	529.9	530.4	531.5	532.5	533.6	534.6
137.5°	544.4	545.8	547.2	548.6	550.0	550.7	551.3	552.4	553.5	554.7	555.8
140°	566.7	567.6	568.6	569.5	570.4	570.9	571.5	572.8	574.1	575.3	576.6
142.5°	585.4	586.2	587.0	587.8	588.6	589.0	589.8	591.3	592.8	594.3	595.8
145°	605.1	605.0	604.9	604.8	604.7	604.6	605.6	607.5	609.5	611.4	613.4
147.5°	622.2	621.8	621.5	621.1	620.8	620.6	621.6	623.6	625.5	627.5	629.5
150°	638.8	638.0	637.2	636.4	635.6	635.2	636.1	638.0	639.8	641.7	643.5
152.5°	652.8	651.9	650.9	650.0	649.1	648.6	649.5	651.2	652.9	654.7	656.4
155°	666.3	665.3	664.2	663.2	662.1	661.6	662.3	663.7	665.0	666.4	667.8
157.5°	677.2	676.3	675.3	674.4	673.5	673.0	673.5	674.6	675.6	676.7	677.7
160°	686.5	685.8	685.1	684.4	683.7	683.4	683.7	684.4	685.1	685.8	686.5
162.5°	694.8	694.1	693.4	692.7	692.0	691.7	692.0	692.6	693.1	693.7	694.3
165°	702.1	701.4	700.7	700.0	699.3	698.9	699.1	699.4	699.8	700.1	700.5
167.5°	707.8	707.1	706.4	705.7	705.0	704.6	704.8	705.1	705.5	705.8	706.2
170°	712.4	711.7	711.0	710.3	709.6	709.3	709.4	709.7	709.9	710.2	710.4
172.5°	715.5	714.8	714.1	713.4	712.7	712.4	712.5	712.8	713.0	713.3	713.5
175°	718.1	717.3	716.5	715.7	714.9	714.5	714.6	714.8	715.1	715.3	715.5
177.5°	719.2	718.4	717.6	716.7	715.9	715.5	715.6	715.7	715.8	716.0	716.1
180°	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6

TEST NUMBER: P1010156

CATALOG NUMBER: S122RDIP-B675D530UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1515.9	1517.9	1521.0	1535.2	1537.3	1541.3	1539.3	1539.3	1540.3	1538.3	1539.3
5°	1581.0	1584.1	1599.3	1616.6	1620.7	1616.6	1621.7	1628.8	1628.8	1628.8	1626.8
7.5°	1642.1	1653.2	1670.5	1696.0	1701.1	1706.2	1715.3	1709.2	1711.2	1720.4	1717.3
10°	1701.1	1717.3	1736.7	1758.0	1769.2	1776.4	1780.4	1789.6	1810.9	1786.5	1795.7
12.5°	1757.0	1780.4	1800.8	1824.2	1832.3	1841.5	1844.5	1852.7	1852.7	1851.6	1858.8
15°	1793.6	1815.0	1833.3	1848.6	1850.6	1848.6	1846.6	1847.6	1850.6	1838.4	1845.5
17.5°	1801.8	1803.8	1809.9	1803.8	1804.8	1783.5	1771.3	1768.2	1739.7	1740.7	1764.1
20°	1762.1	1727.5	1718.4	1684.8	1664.4	1609.5	1607.5	1592.2	1532.2	1550.5	1546.4
22.5°	1653.2	1594.2	1515.9	1477.2	1457.9	1399.9	1355.2	1323.6	1302.3	1280.9	1271.7
25°	1509.8	1414.2	1303.3	1227.0	1215.8	1161.9	1079.4	1040.8	995.0	980.8	1005.2
27.5°	1324.6	1200.5	1075.4	958.4	937.0	888.2	846.5	819.0	766.1	763.0	765.1
30°	1073.3	948.2	843.4	767.1	714.2	691.8	664.4	644.0	622.6	630.8	632.8
32.5°	882.1	763.0	665.4	624.7	600.3	586.0	562.6	549.4	540.2	537.2	536.2
35°	701.0	621.6	577.9	538.2	524.0	513.8	496.5	490.4	482.2	483.3	483.3
37.5°	600.3	534.1	501.6	481.2	468.0	462.9	451.7	445.6	440.5	438.5	441.5
40°	517.8	472.1	451.7	433.4	422.2	420.2	414.1	407.0	400.8	401.9	404.9
42.5°	457.8	431.4	407.0	392.7	384.6	381.5	376.4	371.3	371.3	368.3	367.3
45°	410.0	388.6	368.3	355.1	350.0	345.9	339.8	338.8	334.7	335.7	336.8
47.5°	367.3	350.0	334.7	321.5	316.4	315.4	309.3	305.2	305.2	304.2	303.2
50°	328.6	311.3	298.1	291.0	283.9	281.8	280.8	279.8	277.7	277.7	278.8
52.5°	297.1	279.8	269.6	263.5	259.4	257.4	257.4	256.4	256.4	256.4	255.4
55°	262.5	248.2	240.1	238.1	236.0	235.0	234.0	232.0	230.9	233.0	230.9
57.5°	229.9	224.8	217.7	215.7	210.6	210.6	207.5	205.5	203.5	205.5	205.5
60°	204.5	197.4	193.3	187.2	183.1	179.1	174.0	173.0	170.9	169.9	168.9
62.5°	178.0	171.9	161.8	152.6	146.5	142.4	140.4	139.4	139.4	138.4	138.4
65°	148.5	134.3	129.2	126.2	125.1	124.1	122.1	121.1	122.1	121.1	122.1
67.5°	116.0	113.9	110.9	108.9	107.8	106.8	106.8	105.8	105.8	105.8	105.8
70°	100.7	95.6	94.6	92.6	92.6	91.6	91.6	91.6	91.6	90.5	92.6
72.5°	83.4	80.4	79.4	78.3	78.3	78.3	77.3	77.3	77.3	76.3	77.3
75°	68.2	67.1	65.1	65.1	64.1	65.1	64.1	64.1	63.1	64.1	64.1
77.5°	54.9	53.9	52.9	52.9	51.9	51.9	51.9	51.9	51.9	51.9	52.9
80°	41.7	40.7	39.7	40.7	39.7	40.7	39.7	39.7	40.7	39.7	39.7
82.5°	30.5	29.5	29.5	28.5	28.5	28.5	28.5	28.5	28.5	28.5	28.5
85°	18.3	17.3	17.3	18.3	17.3	18.3	17.3	17.3	17.3	18.3	18.3
87.5°	8.1	9.2	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	9.2
90°	11.0	11.6	12.1	12.7	13.0	13.1	13.3	13.6	13.8	14.0	13.8
92.5°	12.6	12.9	13.1	13.4	13.5	13.6	13.7	13.8	13.9	14.0	13.9
95°	20.8	21.4	21.9	22.5	22.8	22.7	22.6	22.5	22.4	22.3	22.4
97.5°	26.8	27.1	27.5	27.8	28.0	28.1	28.2	28.3	28.4	28.5	28.4
100°	30.5	31.4	32.3	33.2	33.7	33.8	34.0	34.3	34.5	34.7	34.5
102.5°	31.9	33.1	34.4	35.7	36.3	36.5	36.8	37.2	37.5	37.9	37.5
105°	32.9	34.1	35.4	36.7	37.3	37.5	38.0	38.5	38.9	39.4	38.9
107.5°	34.0	35.2	36.5	37.8	38.4	38.6	39.1	39.5	40.0	40.4	40.0
110°	79.2	67.7	56.2	44.7	38.9	39.1	39.6	40.1	40.5	41.0	40.5

TEST NUMBER: P1010156

CATALOG NUMBER: S122RDIP-B675D530UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	213.7	164.1	114.4	64.7	39.9	40.1	40.4	40.8	41.1	41.5	41.1
115°	266.5	213.2	159.8	106.5	79.8	75.7	67.4	59.1	50.8	42.5	50.8
117.5°	331.4	315.0	298.5	282.0	273.8	258.7	228.5	198.3	168.1	137.9	168.1
120°	381.5	382.9	384.2	385.6	386.3	378.5	363.0	347.4	331.9	316.3	331.9
122.5°	411.4	412.1	412.8	413.5	413.8	413.9	414.0	414.1	414.2	414.3	414.2
125°	438.9	439.7	440.6	441.4	441.8	442.0	442.3	442.6	443.0	443.3	443.0
127.5°	464.7	465.8	467.0	468.1	468.7	468.8	468.9	469.0	469.1	469.2	469.1
130°	489.2	490.4	491.7	493.0	493.6	493.5	493.4	493.3	493.2	493.1	493.2
132.5°	513.3	514.3	515.4	516.4	516.9	516.8	516.7	516.6	516.5	516.4	516.5
135°	535.8	536.9	538.1	539.2	539.8	539.7	539.4	539.2	538.9	538.7	538.9
137.5°	557.0	558.1	559.3	560.4	561.0	560.8	560.5	560.2	559.8	559.5	559.8
140°	577.6	578.6	579.7	580.7	581.2	580.9	580.4	579.8	579.3	578.7	579.3
142.5°	596.7	597.6	598.5	599.4	599.9	599.6	599.0	598.5	597.9	597.3	597.9
145°	614.2	615.0	615.8	616.6	617.0	616.7	616.1	615.6	615.0	614.4	615.0
147.5°	630.1	630.7	631.2	631.8	632.1	631.9	631.4	630.9	630.5	630.0	630.5
150°	644.2	644.9	645.6	646.3	646.6	646.3	645.7	645.2	644.6	644.0	644.6
152.5°	657.1	657.8	658.5	659.2	659.5	659.1	658.3	657.5	656.7	655.9	656.7
155°	668.5	669.2	669.9	670.6	670.9	670.4	669.5	668.6	667.7	666.8	667.7
157.5°	678.5	679.3	680.1	680.9	681.3	680.8	679.9	679.0	678.1	677.2	678.1
160°	687.2	687.9	688.6	689.3	689.6	689.2	688.4	687.6	686.8	686.0	686.8
162.5°	695.1	695.9	696.7	697.5	697.9	697.4	696.3	695.3	694.2	693.2	694.2
165°	701.3	702.1	702.9	703.7	704.1	703.7	702.9	702.1	701.3	700.5	701.3
167.5°	707.0	707.8	708.6	709.4	709.8	709.3	708.3	707.2	706.2	705.2	706.2
170°	711.2	712.0	712.8	713.6	714.0	713.5	712.4	711.4	710.3	709.3	710.3
172.5°	714.3	715.1	715.9	716.7	717.1	716.6	715.5	714.5	713.4	712.4	713.4
175°	716.3	717.1	718.0	718.8	719.2	718.6	717.5	716.3	715.2	714.0	715.2
177.5°	716.9	717.7	718.5	719.3	719.7	719.2	718.1	717.1	716.0	715.0	716.0
180°	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6

TEST NUMBER: P1010156

CATALOG NUMBER: S122RDIP-B675D530UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1543.4	1536.2	1534.2	1536.2	1534.2	1535.2	1528.1	1501.7	1508.8	1497.6	1503.7
5°	1630.9	1624.8	1611.5	1609.5	1607.5	1605.4	1595.3	1571.9	1562.7	1547.4	1546.4
7.5°	1714.3	1714.3	1704.1	1697.0	1687.8	1680.7	1667.5	1632.9	1618.7	1600.3	1590.2
10°	1796.7	1770.2	1781.4	1774.3	1751.9	1747.9	1723.4	1703.1	1675.6	1657.3	1641.0
12.5°	1855.7	1847.6	1837.4	1831.3	1825.2	1812.0	1795.7	1743.8	1729.6	1692.9	1674.6
15°	1853.7	1848.6	1851.6	1851.6	1849.6	1846.6	1833.3	1795.7	1771.3	1735.7	1704.1
17.5°	1754.0	1767.2	1780.4	1789.6	1809.9	1819.1	1831.3	1808.9	1793.6	1763.1	1729.6
20°	1580.0	1612.6	1651.2	1659.4	1677.7	1731.6	1756.0	1775.3	1781.4	1771.3	1743.8
22.5°	1337.9	1365.3	1458.9	1456.9	1483.3	1547.4	1618.7	1676.6	1722.4	1747.9	1737.7
25°	1047.9	1086.6	1136.4	1174.1	1260.5	1356.2	1444.7	1537.3	1616.6	1686.8	1704.1
27.5°	792.5	843.4	883.1	932.9	976.7	1089.6	1203.6	1348.0	1440.6	1573.9	1643.1
30°	641.0	664.4	704.0	727.4	748.8	835.3	964.5	1106.9	1269.7	1423.3	1542.4
32.5°	547.4	563.6	593.1	603.3	625.7	683.7	765.1	895.3	1063.2	1249.3	1406.0
35°	491.4	508.7	514.8	524.0	542.3	578.9	634.8	729.5	881.1	1063.2	1250.4
37.5°	443.6	452.7	470.0	476.1	482.2	509.7	547.4	613.5	714.2	863.8	1071.3
40°	410.0	415.1	424.2	429.3	433.4	452.7	486.3	531.1	605.3	719.3	910.6
42.5°	374.4	380.5	386.6	392.7	397.8	413.1	433.4	476.1	526.0	612.5	750.8
45°	339.8	343.9	351.0	355.1	362.2	374.4	392.7	422.2	467.0	521.9	633.8
47.5°	308.3	313.4	316.4	321.5	326.6	339.8	357.1	376.4	413.1	467.0	548.4
50°	279.8	285.9	290.0	291.0	295.0	307.2	321.5	342.9	366.3	408.0	479.2
52.5°	259.4	260.5	263.5	267.6	266.6	273.7	286.9	303.2	327.6	361.2	413.1
55°	236.0	239.1	241.1	242.1	242.1	248.2	255.4	270.6	290.0	317.4	361.2
57.5°	206.5	209.6	215.7	217.7	220.8	223.8	226.9	237.1	253.3	279.8	315.4
60°	176.0	178.0	184.1	188.2	190.3	198.4	202.5	210.6	219.8	239.1	272.7
62.5°	141.4	143.5	146.5	150.6	154.6	166.9	177.0	185.2	192.3	205.5	233.0
65°	123.1	124.1	126.2	127.2	128.2	133.3	142.4	153.6	166.9	177.0	193.3
67.5°	106.8	107.8	108.9	110.9	111.9	112.9	117.0	120.1	133.3	147.5	159.7
70°	91.6	93.6	94.6	94.6	95.6	97.7	99.7	103.8	107.8	115.0	130.2
72.5°	77.3	78.3	80.4	80.4	80.4	82.4	84.4	86.5	88.5	92.6	98.7
75°	64.1	66.1	66.1	66.1	67.1	67.1	69.2	71.2	73.3	76.3	78.3
77.5°	52.9	52.9	52.9	52.9	53.9	53.9	54.9	57.0	58.0	59.0	61.0
80°	39.7	40.7	40.7	40.7	41.7	41.7	41.7	43.7	44.8	44.8	46.8
82.5°	29.5	29.5	29.5	30.5	29.5	30.5	30.5	31.5	30.5	31.5	32.6
85°	18.3	18.3	18.3	19.3	19.3	19.3	19.3	19.3	19.3	19.3	20.3
87.5°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	10.2	9.2	9.2
90°	13.6	13.3	13.1	13.0	12.7	12.1	11.6	11.0	10.4	9.5	8.5
92.5°	13.8	13.7	13.6	13.5	13.4	13.1	12.9	12.6	12.4	12.1	11.7
95°	22.5	22.6	22.7	22.8	22.5	21.9	21.4	20.8	20.2	19.4	18.6
97.5°	28.3	28.2	28.1	28.0	27.8	27.5	27.1	26.8	26.4	24.6	22.7
100°	34.3	34.0	33.8	33.7	33.2	32.3	31.4	30.5	29.6	27.6	25.6
102.5°	37.2	36.8	36.5	36.3	35.7	34.4	33.1	31.9	30.6	51.6	72.6
105°	38.5	38.0	37.5	37.3	36.7	35.4	34.1	32.9	31.6	63.1	94.5
107.5°	39.5	39.1	38.6	38.4	37.8	36.5	35.2	34.0	32.7	71.5	110.3
110°	40.1	39.6	39.1	38.9	44.7	56.2	67.7	79.2	90.7	124.0	157.3

TEST NUMBER: P1010156

CATALOG NUMBER: S122RDIP-B675D530UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	40.8	40.4	40.1	39.9	64.7	114.4	164.1	213.7	263.4	265.4	267.3
115°	59.1	67.4	75.7	79.8	106.5	159.8	213.2	266.5	319.9	317.0	314.2
117.5°	198.3	228.5	258.7	273.8	282.0	298.5	315.0	331.4	347.9	345.9	344.0
120°	347.4	363.0	378.5	386.3	385.6	384.2	382.9	381.5	380.1	378.0	375.9
122.5°	414.1	414.0	413.9	413.8	413.5	412.8	412.1	411.4	410.7	408.4	406.1
125°	442.6	442.3	442.0	441.8	441.4	440.6	439.7	438.9	438.1	435.9	433.7
127.5°	469.0	468.9	468.8	468.7	468.1	467.0	465.8	464.7	463.5	461.8	460.1
130°	493.3	493.4	493.5	493.6	493.0	491.7	490.4	489.2	487.9	486.6	485.4
132.5°	516.6	516.7	516.8	516.9	516.4	515.4	514.3	513.3	512.3	511.0	509.8
135°	539.2	539.4	539.7	539.8	539.2	538.1	536.9	535.8	534.6	533.6	532.5
137.5°	560.2	560.5	560.8	561.0	560.4	559.3	558.1	557.0	555.8	554.7	553.5
140°	579.8	580.4	580.9	581.2	580.7	579.7	578.6	577.6	576.6	575.3	574.1
142.5°	598.5	599.0	599.6	599.9	599.4	598.5	597.6	596.7	595.8	594.3	592.8
145°	615.6	616.1	616.7	617.0	616.6	615.8	615.0	614.2	613.4	611.4	609.5
147.5°	630.9	631.4	631.9	632.1	631.8	631.2	630.7	630.1	629.5	627.5	625.5
150°	645.2	645.7	646.3	646.6	646.3	645.6	644.9	644.2	643.5	641.7	639.8
152.5°	657.5	658.3	659.1	659.5	659.2	658.5	657.8	657.1	656.4	654.7	652.9
155°	668.6	669.5	670.4	670.9	670.6	669.9	669.2	668.5	667.8	666.4	665.0
157.5°	679.0	679.9	680.8	681.3	680.9	680.1	679.3	678.5	677.7	676.7	675.6
160°	687.6	688.4	689.2	689.6	689.3	688.6	687.9	687.2	686.5	685.8	685.1
162.5°	695.3	696.3	697.4	697.9	697.5	696.7	695.9	695.1	694.3	693.7	693.1
165°	702.1	702.9	703.7	704.1	703.7	702.9	702.1	701.3	700.5	700.1	699.8
167.5°	707.2	708.3	709.3	709.8	709.4	708.6	707.8	707.0	706.2	705.8	705.5
170°	711.4	712.4	713.5	714.0	713.6	712.8	712.0	711.2	710.4	710.2	709.9
172.5°	714.5	715.5	716.6	717.1	716.7	715.9	715.1	714.3	713.5	713.3	713.0
175°	716.3	717.5	718.6	719.2	718.8	718.0	717.1	716.3	715.5	715.3	715.1
177.5°	717.1	718.1	719.2	719.7	719.3	718.5	717.7	716.9	716.1	716.0	715.8
180°	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6

TEST NUMBER: P1010156

CATALOG NUMBER: S122RDIP-B675D530UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1494.5	1489.4	1489.4	1486.4	1486.4	1470.1	1470.1	1475.2	1469.1	1462.0	1451.8
5°	1533.2	1522.0	1519.0	1514.9	1501.7	1481.3	1473.2	1470.1	1457.9	1442.7	1425.4
7.5°	1569.8	1551.5	1542.4	1533.2	1515.9	1487.4	1471.1	1459.9	1441.6	1418.2	1395.9
10°	1605.4	1582.0	1558.6	1547.4	1523.0	1487.4	1464.0	1445.7	1419.3	1387.7	1356.2
12.5°	1638.0	1589.2	1585.1	1562.7	1527.1	1486.4	1450.8	1424.3	1390.8	1354.1	1317.5
15°	1666.5	1616.6	1592.2	1571.9	1525.1	1474.2	1436.5	1404.0	1359.2	1317.5	1272.7
17.5°	1680.7	1626.8	1610.5	1576.9	1529.1	1463.0	1412.1	1372.5	1323.6	1273.8	1222.9
20°	1695.0	1631.9	1605.4	1582.0	1516.9	1441.6	1384.7	1338.9	1285.0	1225.9	1170.0
22.5°	1702.1	1631.9	1600.3	1567.8	1504.7	1418.2	1351.1	1297.2	1234.1	1174.1	1106.9
25°	1689.9	1625.8	1588.1	1554.6	1483.3	1389.7	1312.4	1251.4	1184.2	1116.1	1047.9
27.5°	1659.4	1611.5	1567.8	1533.2	1453.8	1353.1	1271.7	1202.5	1133.4	1057.1	987.9
30°	1602.4	1581.0	1546.4	1507.8	1421.3	1320.6	1223.9	1152.7	1076.4	1000.1	927.9
32.5°	1513.9	1532.2	1509.8	1476.2	1382.6	1275.8	1173.0	1100.8	1017.4	935.0	868.8
35°	1406.0	1471.1	1458.9	1435.5	1341.9	1228.0	1125.2	1037.7	954.3	870.9	804.8
37.5°	1288.0	1386.7	1396.9	1382.6	1295.1	1179.1	1066.2	980.8	895.3	810.9	743.7
40°	1126.2	1277.8	1310.4	1316.5	1246.3	1120.1	1002.1	918.7	834.3	751.8	670.5
42.5°	977.7	1169.0	1209.7	1235.1	1184.2	1062.1	943.1	850.5	767.1	692.8	611.4
45°	838.3	1037.7	1103.9	1136.4	1114.0	996.0	872.9	786.4	710.1	642.0	563.6
47.5°	694.9	895.3	987.9	1039.8	1039.8	928.9	805.8	720.3	647.1	589.1	519.9
50°	599.2	766.1	861.7	929.9	948.2	860.7	744.7	661.3	592.1	529.0	476.1
52.5°	510.7	660.3	739.6	810.9	863.8	787.5	676.6	601.3	533.1	474.1	432.4
55°	441.5	553.5	625.7	704.0	763.0	713.2	610.4	537.2	478.2	429.3	393.7
57.5°	375.4	473.1	532.1	601.3	664.4	626.7	544.3	481.2	429.3	386.6	355.1
60°	319.5	398.8	444.6	498.5	576.9	550.4	482.2	424.2	382.5	343.9	317.4
62.5°	271.6	334.7	373.4	412.0	483.3	471.0	418.1	373.4	337.8	305.2	282.8
65°	222.8	274.7	305.2	338.8	395.8	400.8	358.1	326.6	294.0	265.5	245.2
67.5°	180.1	220.8	248.2	276.7	322.5	336.8	307.2	280.8	253.3	229.9	211.6
70°	145.5	174.0	194.3	216.7	254.3	271.6	256.4	238.1	215.7	196.4	180.1
72.5°	115.0	133.3	145.5	162.8	193.3	210.6	209.6	193.3	177.0	163.8	150.6
75°	84.4	98.7	108.9	120.1	144.5	160.7	164.8	157.7	141.4	131.2	121.1
77.5°	64.1	72.2	77.3	85.5	102.8	117.0	123.1	121.1	109.9	101.7	94.6
80°	48.8	50.9	52.9	56.0	70.2	83.4	87.5	86.5	80.4	77.3	69.2
82.5°	34.6	35.6	36.6	37.6	42.7	53.9	58.0	60.0	54.9	51.9	44.8
85°	20.3	21.4	21.4	23.4	24.4	27.5	34.6	34.6	33.6	29.5	28.5
87.5°	10.2	10.2	9.2	9.2	10.2	11.2	13.2	15.3	13.2	12.2	11.2
90°	7.6	6.7	6.2	5.6	4.3	3.0	1.8	0.5	1.8	3.0	4.3
92.5°	11.4	11.1	10.9	11.1	11.6	12.1	12.5	13.0	12.5	12.1	11.6
95°	17.8	17.0	16.6	18.5	22.3	26.1	29.9	33.7	29.9	26.1	22.3
97.5°	20.9	19.0	18.1	22.8	32.3	41.8	51.2	60.7	51.2	41.8	32.3
100°	23.7	21.7	20.7	28.6	44.4	60.2	76.0	91.8	76.0	60.2	44.4
102.5°	93.5	114.5	125.0	125.1	125.3	125.6	125.8	126.0	125.8	125.6	125.3
105°	126.0	157.5	173.2	171.5	168.0	164.5	161.1	157.6	161.1	164.5	168.0
107.5°	149.2	188.0	207.4	206.0	203.1	200.2	197.3	194.4	197.3	200.2	203.1
110°	190.6	223.9	240.6	239.4	237.0	234.5	232.1	229.7	232.1	234.5	237.0

TEST NUMBER: P1010156

CATALOG NUMBER: S122RDIP-B675D530UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	269.3	271.2	272.2	271.2	269.1	267.0	265.0	262.9	265.0	267.0	269.1
115°	311.3	308.4	307.0	306.0	304.0	302.1	300.1	298.1	300.1	302.1	304.0
117.5°	342.0	340.1	339.1	337.9	335.6	333.3	331.0	328.7	331.0	333.3	335.6
120°	373.8	371.7	370.7	369.8	368.1	366.4	364.7	363.0	364.7	366.4	368.1
122.5°	403.8	401.5	400.3	399.4	397.5	395.7	393.8	392.0	393.8	395.7	397.5
125°	431.6	429.4	428.3	427.5	426.0	424.5	423.0	421.5	423.0	424.5	426.0
127.5°	458.4	456.7	455.8	455.0	453.4	451.7	450.1	448.5	450.1	451.7	453.4
130°	484.1	482.8	482.2	481.3	479.4	477.6	475.7	473.9	475.7	477.6	479.4
132.5°	508.5	507.2	506.6	505.8	504.3	502.8	501.3	499.8	501.3	502.8	504.3
135°	531.5	530.4	529.9	529.0	527.1	525.3	523.4	521.6	523.4	525.3	527.1
137.5°	552.4	551.3	550.7	550.0	548.6	547.2	545.8	544.4	545.8	547.2	548.6
140°	572.8	571.5	570.9	570.4	569.5	568.6	567.6	566.7	567.6	568.6	569.5
142.5°	591.3	589.8	589.0	588.6	587.8	587.0	586.2	585.4	586.2	587.0	587.8
145°	607.5	605.6	604.6	604.7	604.8	604.9	605.0	605.1	605.0	604.9	604.8
147.5°	623.6	621.6	620.6	620.8	621.1	621.5	621.8	622.2	621.8	621.5	621.1
150°	638.0	636.1	635.2	635.6	636.4	637.2	638.0	638.8	638.0	637.2	636.4
152.5°	651.2	649.5	648.6	649.1	650.0	650.9	651.9	652.8	651.9	650.9	650.0
155°	663.7	662.3	661.6	662.1	663.2	664.2	665.3	666.3	665.3	664.2	663.2
157.5°	674.6	673.5	673.0	673.5	674.4	675.3	676.3	677.2	676.3	675.3	674.4
160°	684.4	683.7	683.4	683.7	684.4	685.1	685.8	686.5	685.8	685.1	684.4
162.5°	692.6	692.0	691.7	692.0	692.7	693.4	694.1	694.8	694.1	693.4	692.7
165°	699.4	699.1	698.9	699.3	700.0	700.7	701.4	702.1	701.4	700.7	700.0
167.5°	705.1	704.8	704.6	705.0	705.7	706.4	707.1	707.8	707.1	706.4	705.7
170°	709.7	709.4	709.3	709.6	710.3	711.0	711.7	712.4	711.7	711.0	710.3
172.5°	712.8	712.5	712.4	712.7	713.4	714.1	714.8	715.5	714.8	714.1	713.4
175°	714.8	714.6	714.5	714.9	715.7	716.5	717.3	718.1	717.3	716.5	715.7
177.5°	715.7	715.6	715.5	715.9	716.7	717.6	718.4	719.2	718.4	717.6	716.7
180°	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6

TEST NUMBER: P1010156

CATALOG NUMBER: S122RDIP-B675D530UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1447.7	1448.8	1451.8	1442.7	1428.4	1422.3	1404.0	1400.9	1397.9	1397.9	1400.9
5°	1415.2	1411.1	1412.1	1394.8	1374.5	1362.3	1336.8	1340.9	1327.7	1319.5	1321.6
7.5°	1379.6	1368.4	1367.4	1345.0	1319.5	1297.2	1270.7	1264.6	1252.4	1238.2	1232.1
10°	1334.8	1326.7	1311.4	1286.0	1253.4	1235.1	1199.5	1178.1	1175.1	1153.7	1145.6
12.5°	1289.0	1274.8	1259.5	1223.9	1187.3	1157.8	1131.3	1107.9	1091.7	1073.3	1061.1
15°	1236.1	1218.8	1201.5	1163.9	1121.2	1091.7	1052.0	1017.4	969.6	931.9	910.6
17.5°	1178.1	1158.8	1135.4	1093.7	1052.0	1011.3	938.0	897.3	863.8	841.4	828.2
20°	1118.1	1096.7	1073.3	1031.6	959.4	888.2	847.5	815.9	795.6	773.2	756.9
22.5°	1055.0	1032.6	1007.2	942.1	865.8	815.9	784.4	754.9	725.4	713.2	705.0
25°	996.0	975.7	943.1	854.6	794.6	748.8	713.2	693.9	678.6	662.3	647.1
27.5°	935.0	897.3	851.6	777.3	739.6	692.8	667.4	653.2	626.7	615.5	608.4
30°	861.7	820.0	776.3	723.4	679.6	647.1	623.7	600.3	585.0	573.8	561.6
32.5°	787.5	747.8	720.3	665.4	632.8	599.2	576.9	562.6	540.2	533.1	528.0
35°	723.4	689.8	665.4	620.6	590.1	559.6	543.3	521.9	507.7	494.4	486.3
37.5°	660.3	642.0	616.5	578.9	546.3	521.9	499.5	492.4	473.1	466.0	457.8
40°	616.5	589.1	567.7	535.1	507.7	481.2	467.0	450.7	437.5	426.3	423.2
42.5°	563.6	543.3	531.1	495.5	467.0	451.7	434.4	416.1	405.9	396.8	385.6
45°	524.0	505.6	488.3	459.9	434.4	415.1	399.8	387.6	370.3	366.3	349.0
47.5°	482.2	463.9	450.7	422.2	398.8	380.5	369.3	353.0	338.8	329.6	321.5
50°	440.5	425.3	413.1	388.6	368.3	349.0	333.7	317.4	311.3	296.1	291.0
52.5°	400.8	390.7	377.4	354.0	333.7	317.4	301.1	287.9	278.8	270.6	264.5
55°	367.3	351.0	344.9	319.5	302.2	284.9	270.6	262.5	251.3	246.2	241.1
57.5°	329.6	320.5	310.3	291.0	271.6	255.4	245.2	233.0	226.9	220.8	216.7
60°	297.1	283.9	275.7	259.4	242.1	226.9	217.7	208.6	200.4	195.3	187.2
62.5°	259.4	249.3	244.2	226.9	212.6	198.4	190.3	181.1	175.0	165.8	155.7
65°	226.9	218.7	212.6	198.4	185.2	171.9	163.8	152.6	144.5	139.4	138.4
67.5°	198.4	192.3	183.1	169.9	156.7	146.5	137.3	128.2	127.2	125.1	125.1
70°	166.9	160.7	155.7	141.4	130.2	119.0	117.0	113.9	110.9	109.9	107.8
72.5°	139.4	134.3	128.2	116.0	104.8	101.7	99.7	97.7	94.6	93.6	92.6
75°	112.9	105.8	101.7	90.5	87.5	85.5	83.4	80.4	78.3	77.3	75.3
77.5°	86.5	79.4	79.4	73.3	71.2	68.2	66.1	64.1	63.1	61.0	61.0
80°	61.0	61.0	59.0	56.0	52.9	51.9	48.8	47.8	46.8	47.8	45.8
82.5°	44.8	40.7	40.7	38.7	36.6	35.6	33.6	33.6	32.6	32.6	32.6
85°	25.4	25.4	24.4	22.4	21.4	21.4	20.3	20.3	19.3	19.3	18.3
87.5°	10.2	9.2	10.2	9.2	9.2	8.1	8.1	8.1	7.1	8.1	7.1
90°	5.6	6.2	6.7	7.6	8.5	9.5	10.4	11.0	11.6	12.1	12.7
92.5°	11.1	10.9	11.1	11.4	11.7	12.1	12.4	12.6	12.9	13.1	13.4
95°	18.5	16.6	17.0	17.8	18.6	19.4	20.2	20.8	21.4	21.9	22.5
97.5°	22.8	18.1	19.0	20.9	22.7	24.6	26.4	26.8	27.1	27.5	27.8
100°	28.6	20.7	21.7	23.7	25.6	27.6	29.6	30.5	31.4	32.3	33.2
102.5°	125.1	125.0	114.5	93.5	72.6	51.6	30.6	31.9	33.1	34.4	35.7
105°	171.5	173.2	157.5	126.0	94.5	63.1	31.6	32.9	34.1	35.4	36.7
107.5°	206.0	207.4	188.0	149.2	110.3	71.5	32.7	34.0	35.2	36.5	37.8
110°	239.4	240.6	223.9	190.6	157.3	124.0	90.7	79.2	67.7	56.2	44.7

TEST NUMBER: P1010156

CATALOG NUMBER: S122RDIP-B675D530UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	271.2	272.2	271.2	269.3	267.3	265.4	263.4	213.7	164.1	114.4	64.7
115°	306.0	307.0	308.4	311.3	314.2	317.0	319.9	266.5	213.2	159.8	106.5
117.5°	337.9	339.1	340.1	342.0	344.0	345.9	347.9	331.4	315.0	298.5	282.0
120°	369.8	370.7	371.7	373.8	375.9	378.0	380.1	381.5	382.9	384.2	385.6
122.5°	399.4	400.3	401.5	403.8	406.1	408.4	410.7	411.4	412.1	412.8	413.5
125°	427.5	428.3	429.4	431.6	433.7	435.9	438.1	438.9	439.7	440.6	441.4
127.5°	455.0	455.8	456.7	458.4	460.1	461.8	463.5	464.7	465.8	467.0	468.1
130°	481.3	482.2	482.8	484.1	485.4	486.6	487.9	489.2	490.4	491.7	493.0
132.5°	505.8	506.6	507.2	508.5	509.8	511.0	512.3	513.3	514.3	515.4	516.4
135°	529.0	529.9	530.4	531.5	532.5	533.6	534.6	535.8	536.9	538.1	539.2
137.5°	550.0	550.7	551.3	552.4	553.5	554.7	555.8	557.0	558.1	559.3	560.4
140°	570.4	570.9	571.5	572.8	574.1	575.3	576.6	577.6	578.6	579.7	580.7
142.5°	588.6	589.0	589.8	591.3	592.8	594.3	595.8	596.7	597.6	598.5	599.4
145°	604.7	604.6	605.6	607.5	609.5	611.4	613.4	614.2	615.0	615.8	616.6
147.5°	620.8	620.6	621.6	623.6	625.5	627.5	629.5	630.1	630.7	631.2	631.8
150°	635.6	635.2	636.1	638.0	639.8	641.7	643.5	644.2	644.9	645.6	646.3
152.5°	649.1	648.6	649.5	651.2	652.9	654.7	656.4	657.1	657.8	658.5	659.2
155°	662.1	661.6	662.3	663.7	665.0	666.4	667.8	668.5	669.2	669.9	670.6
157.5°	673.5	673.0	673.5	674.6	675.6	676.7	677.7	678.5	679.3	680.1	680.9
160°	683.7	683.4	683.7	684.4	685.1	685.8	686.5	687.2	687.9	688.6	689.3
162.5°	692.0	691.7	692.0	692.6	693.1	693.7	694.3	695.1	695.9	696.7	697.5
165°	699.3	698.9	699.1	699.4	699.8	700.1	700.5	701.3	702.1	702.9	703.7
167.5°	705.0	704.6	704.8	705.1	705.5	705.8	706.2	707.0	707.8	708.6	709.4
170°	709.6	709.3	709.4	709.7	709.9	710.2	710.4	711.2	712.0	712.8	713.6
172.5°	712.7	712.4	712.5	712.8	713.0	713.3	713.5	714.3	715.1	715.9	716.7
175°	714.9	714.5	714.6	714.8	715.1	715.3	715.5	716.3	717.1	718.0	718.8
177.5°	715.9	715.5	715.6	715.7	715.8	716.0	716.1	716.9	717.7	718.5	719.3
180°	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6

TEST NUMBER: P1010156

CATALOG NUMBER: S122RDIP-B675D530UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1400.9	1398.9	1392.8	1394.8	1391.8	1391.8	1389.7	1389.7	1389.7	1394.8	1391.8
5°	1324.6	1317.5	1310.4	1307.3	1304.3	1301.2	1301.2	1300.2	1309.4	1307.3	1315.5
7.5°	1230.0	1228.0	1213.7	1213.7	1208.7	1206.6	1211.7	1212.7	1213.7	1215.8	1220.9
10°	1145.6	1140.5	1120.1	1122.2	1119.1	1115.1	1118.1	1116.1	1123.2	1125.2	1123.2
12.5°	1045.9	1036.7	1014.3	1003.1	990.9	981.8	993.0	984.8	1013.3	1021.5	1043.8
15°	913.6	896.3	881.1	881.1	869.9	861.7	866.8	876.0	882.1	891.2	895.3
17.5°	825.1	818.0	805.8	798.6	795.6	792.5	792.5	796.6	809.8	808.8	817.0
20°	749.8	745.7	739.6	730.5	727.4	725.4	725.4	725.4	734.6	742.7	747.8
22.5°	697.9	694.9	690.8	678.6	672.5	670.5	675.5	678.6	685.7	691.8	696.9
25°	646.0	638.9	631.8	627.7	624.7	624.7	626.7	627.7	630.8	633.8	639.9
27.5°	603.3	598.2	588.0	576.9	576.9	573.8	575.8	577.9	585.0	595.2	600.3
30°	555.5	554.5	550.4	546.3	542.3	540.2	544.3	547.4	548.4	553.5	553.5
32.5°	520.9	513.8	506.7	502.6	500.6	499.5	500.6	504.6	504.6	510.7	517.8
35°	486.3	482.2	475.1	468.0	466.0	460.9	464.9	469.0	476.1	479.2	482.2
37.5°	448.7	443.6	440.5	438.5	434.4	435.4	432.4	438.5	444.6	443.6	445.6
40°	420.2	411.0	401.9	400.8	399.8	398.8	398.8	399.8	403.9	408.0	414.1
42.5°	383.6	380.5	372.4	364.2	362.2	360.2	358.1	362.2	370.3	377.4	380.5
45°	345.9	341.8	339.8	333.7	329.6	328.6	326.6	331.7	338.8	341.8	343.9
47.5°	311.3	310.3	304.2	305.2	302.2	303.2	302.2	305.2	305.2	308.3	310.3
50°	287.9	284.9	281.8	279.8	276.7	276.7	275.7	276.7	280.8	284.9	283.9
52.5°	264.5	259.4	258.4	257.4	255.4	257.4	254.3	255.4	259.4	261.5	260.5
55°	237.1	236.0	234.0	232.0	230.9	229.9	229.9	229.9	234.0	237.1	238.1
57.5°	215.7	210.6	206.5	206.5	202.5	201.4	203.5	204.5	207.5	209.6	211.6
60°	186.2	184.1	178.0	175.0	168.9	167.9	167.9	171.9	177.0	184.1	186.2
62.5°	154.6	151.6	150.6	150.6	150.6	150.6	150.6	150.6	150.6	151.6	151.6
65°	137.3	138.4	137.3	136.3	137.3	137.3	136.3	136.3	136.3	137.3	138.4
67.5°	123.1	122.1	123.1	122.1	121.1	121.1	120.1	121.1	122.1	123.1	123.1
70°	106.8	106.8	105.8	106.8	105.8	104.8	103.8	103.8	105.8	106.8	106.8
72.5°	91.6	91.6	90.5	90.5	88.5	88.5	89.5	88.5	88.5	91.6	91.6
75°	76.3	75.3	74.3	74.3	73.3	73.3	73.3	72.2	74.3	74.3	75.3
77.5°	60.0	60.0	60.0	59.0	59.0	58.0	58.0	59.0	59.0	59.0	60.0
80°	45.8	45.8	45.8	44.8	43.7	43.7	43.7	43.7	43.7	44.8	43.7
82.5°	31.5	31.5	31.5	31.5	31.5	30.5	30.5	30.5	31.5	31.5	30.5
85°	19.3	18.3	19.3	19.3	18.3	19.3	18.3	18.3	17.3	17.3	18.3
87.5°	8.1	7.1	6.1	6.1	7.1	6.1	6.1	6.1	7.1	6.1	6.1
90°	13.0	13.1	13.3	13.6	13.8	14.0	13.8	13.6	13.3	13.1	13.0
92.5°	13.5	13.6	13.7	13.8	13.9	14.0	13.9	13.8	13.7	13.6	13.5
95°	22.8	22.7	22.6	22.5	22.4	22.3	22.4	22.5	22.6	22.7	22.8
97.5°	28.0	28.1	28.2	28.3	28.4	28.5	28.4	28.3	28.2	28.1	28.0
100°	33.7	33.8	34.0	34.3	34.5	34.7	34.5	34.3	34.0	33.8	33.7
102.5°	36.3	36.5	36.8	37.2	37.5	37.9	37.5	37.2	36.8	36.5	36.3
105°	37.3	37.5	38.0	38.5	38.9	39.4	38.9	38.5	38.0	37.5	37.3
107.5°	38.4	38.6	39.1	39.5	40.0	40.4	40.0	39.5	39.1	38.6	38.4
110°	38.9	39.1	39.6	40.1	40.5	41.0	40.5	40.1	39.6	39.1	38.9

TEST NUMBER: P1010156

CATALOG NUMBER: S122RDIP-B675D530UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	39.9	40.1	40.4	40.8	41.1	41.5	41.1	40.8	40.4	40.1	39.9
115°	79.8	75.7	67.4	59.1	50.8	42.5	50.8	59.1	67.4	75.7	79.8
117.5°	273.8	258.7	228.5	198.3	168.1	137.9	168.1	198.3	228.5	258.7	273.8
120°	386.3	378.5	363.0	347.4	331.9	316.3	331.9	347.4	363.0	378.5	386.3
122.5°	413.8	413.9	414.0	414.1	414.2	414.3	414.2	414.1	414.0	413.9	413.8
125°	441.8	442.0	442.3	442.6	443.0	443.3	443.0	442.6	442.3	442.0	441.8
127.5°	468.7	468.8	468.9	469.0	469.1	469.2	469.1	469.0	468.9	468.8	468.7
130°	493.6	493.5	493.4	493.3	493.2	493.1	493.2	493.3	493.4	493.5	493.6
132.5°	516.9	516.8	516.7	516.6	516.5	516.4	516.5	516.6	516.7	516.8	516.9
135°	539.8	539.7	539.4	539.2	538.9	538.7	538.9	539.2	539.4	539.7	539.8
137.5°	561.0	560.8	560.5	560.2	559.8	559.5	559.8	560.2	560.5	560.8	561.0
140°	581.2	580.9	580.4	579.8	579.3	578.7	579.3	579.8	580.4	580.9	581.2
142.5°	599.9	599.6	599.0	598.5	597.9	597.3	597.9	598.5	599.0	599.6	599.9
145°	617.0	616.7	616.1	615.6	615.0	614.4	615.0	615.6	616.1	616.7	617.0
147.5°	632.1	631.9	631.4	630.9	630.5	630.0	630.5	630.9	631.4	631.9	632.1
150°	646.6	646.3	645.7	645.2	644.6	644.0	644.6	645.2	645.7	646.3	646.6
152.5°	659.5	659.1	658.3	657.5	656.7	655.9	656.7	657.5	658.3	659.1	659.5
155°	670.9	670.4	669.5	668.6	667.7	666.8	667.7	668.6	669.5	670.4	670.9
157.5°	681.3	680.8	679.9	679.0	678.1	677.2	678.1	679.0	679.9	680.8	681.3
160°	689.6	689.2	688.4	687.6	686.8	686.0	686.8	687.6	688.4	689.2	689.6
162.5°	697.9	697.4	696.3	695.3	694.2	693.2	694.2	695.3	696.3	697.4	697.9
165°	704.1	703.7	702.9	702.1	701.3	700.5	701.3	702.1	702.9	703.7	704.1
167.5°	709.8	709.3	708.3	707.2	706.2	705.2	706.2	707.2	708.3	709.3	709.8
170°	714.0	713.5	712.4	711.4	710.3	709.3	710.3	711.4	712.4	713.5	714.0
172.5°	717.1	716.6	715.5	714.5	713.4	712.4	713.4	714.5	715.5	716.6	717.1
175°	719.2	718.6	717.5	716.3	715.2	714.0	715.2	716.3	717.5	718.6	719.2
177.5°	719.7	719.2	718.1	717.1	716.0	715.0	716.0	717.1	718.1	719.2	719.7
180°	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6

TEST NUMBER: P1010156

CATALOG NUMBER: S122RDIP-B675D530UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1394.8	1399.9	1397.9	1386.7	1397.9	1400.9	1407.0	1413.1	1417.2	1423.3	1428.4
5°	1307.3	1317.5	1323.6	1317.5	1337.9	1340.9	1355.2	1363.3	1375.5	1385.7	1393.8
7.5°	1224.9	1233.1	1245.3	1247.3	1259.5	1273.8	1294.1	1314.5	1333.8	1344.0	1353.1
10°	1136.4	1150.7	1169.0	1164.9	1183.2	1205.6	1227.0	1259.5	1275.8	1294.1	1310.4
12.5°	1047.9	1057.1	1081.5	1089.6	1116.1	1133.4	1162.9	1183.2	1223.9	1245.3	1259.5
15°	893.3	930.9	961.4	998.1	1032.6	1065.2	1091.7	1128.3	1163.9	1180.2	1203.6
17.5°	823.1	840.4	858.7	877.0	921.7	979.7	1026.5	1066.2	1096.7	1118.1	1145.6
20°	749.8	767.1	787.5	804.8	832.2	873.9	931.9	1000.1	1036.7	1059.1	1085.5
22.5°	697.9	714.2	727.4	742.7	764.1	794.6	838.3	922.8	971.6	999.1	1022.5
25°	642.0	662.3	676.6	687.8	705.0	738.6	774.2	822.0	909.5	930.9	963.5
27.5°	603.3	609.4	625.7	643.0	660.3	678.6	715.2	755.9	814.9	861.7	901.4
30°	557.5	572.8	588.0	595.2	610.4	636.9	659.3	703.0	748.8	785.4	833.2
32.5°	522.9	532.1	542.3	559.6	573.8	592.1	614.5	651.1	689.8	713.2	749.8
35°	484.3	490.4	511.7	518.9	533.1	551.4	573.8	602.3	644.0	662.3	688.8
37.5°	447.6	461.9	468.0	484.3	497.5	515.8	532.1	564.6	592.1	613.5	637.9
40°	419.2	425.3	436.5	450.7	461.9	476.1	496.5	519.9	549.4	566.7	588.0
42.5°	384.6	389.7	403.9	412.0	430.4	443.6	455.8	484.3	510.7	524.0	545.3
45°	346.9	359.1	368.3	384.6	394.7	411.0	426.3	446.6	471.0	486.3	498.5
47.5°	314.4	326.6	335.7	351.0	367.3	374.4	390.7	412.0	434.4	446.6	463.9
50°	287.9	292.0	309.3	316.4	333.7	347.9	359.1	377.4	401.9	409.0	423.2
52.5°	262.5	265.5	276.7	285.9	301.1	313.4	327.6	344.9	365.2	376.4	387.6
55°	240.1	242.1	247.2	257.4	267.6	282.8	296.1	312.3	329.6	341.8	352.0
57.5°	214.7	218.7	222.8	228.9	239.1	253.3	267.6	282.8	297.1	305.2	318.4
60°	185.2	191.3	198.4	205.5	212.6	222.8	239.1	253.3	266.6	273.7	283.9
62.5°	153.6	165.8	171.9	180.1	186.2	195.3	207.5	223.8	233.0	242.1	250.3
65°	138.4	139.4	140.4	148.5	159.7	168.9	180.1	192.3	206.5	212.6	218.7
67.5°	123.1	124.1	126.2	127.2	131.2	141.4	153.6	166.9	178.0	182.1	188.2
70°	107.8	107.8	111.9	112.9	113.9	115.0	125.1	138.4	148.5	153.6	160.7
72.5°	91.6	92.6	94.6	95.6	97.7	99.7	102.8	109.9	122.1	127.2	135.3
75°	75.3	76.3	77.3	78.3	81.4	82.4	85.5	89.5	94.6	100.7	105.8
77.5°	60.0	60.0	61.0	63.1	65.1	66.1	69.2	71.2	73.3	76.3	80.4
80°	44.8	45.8	45.8	47.8	47.8	48.8	49.9	52.9	54.9	57.0	59.0
82.5°	30.5	32.6	32.6	32.6	33.6	34.6	35.6	35.6	37.6	38.7	41.7
85°	18.3	19.3	19.3	19.3	18.3	20.3	20.3	21.4	21.4	21.4	22.4
87.5°	7.1	6.1	7.1	7.1	7.1	8.1	7.1	7.1	8.1	9.2	9.2
90°	12.7	12.1	11.6	11.0	10.4	9.5	8.5	7.6	6.7	6.2	5.6
92.5°	13.4	13.1	12.9	12.6	12.4	12.1	11.7	11.4	11.1	10.9	11.1
95°	22.5	21.9	21.4	20.8	20.2	19.4	18.6	17.8	17.0	16.6	18.5
97.5°	27.8	27.5	27.1	26.8	26.4	24.6	22.7	20.9	19.0	18.1	22.8
100°	33.2	32.3	31.4	30.5	29.6	27.6	25.6	23.7	21.7	20.7	28.6
102.5°	35.7	34.4	33.1	31.9	30.6	51.6	72.6	93.5	114.5	125.0	125.1
105°	36.7	35.4	34.1	32.9	31.6	63.1	94.5	126.0	157.5	173.2	171.5
107.5°	37.8	36.5	35.2	34.0	32.7	71.5	110.3	149.2	188.0	207.4	206.0
110°	44.7	56.2	67.7	79.2	90.7	124.0	157.3	190.6	223.9	240.6	239.4

TEST NUMBER: P1010156

CATALOG NUMBER: S122RDIP-B675D530UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	64.7	114.4	164.1	213.7	263.4	265.4	267.3	269.3	271.2	272.2	271.2
115°	106.5	159.8	213.2	266.5	319.9	317.0	314.2	311.3	308.4	307.0	306.0
117.5°	282.0	298.5	315.0	331.4	347.9	345.9	344.0	342.0	340.1	339.1	337.9
120°	385.6	384.2	382.9	381.5	380.1	378.0	375.9	373.8	371.7	370.7	369.8
122.5°	413.5	412.8	412.1	411.4	410.7	408.4	406.1	403.8	401.5	400.3	399.4
125°	441.4	440.6	439.7	438.9	438.1	435.9	433.7	431.6	429.4	428.3	427.5
127.5°	468.1	467.0	465.8	464.7	463.5	461.8	460.1	458.4	456.7	455.8	455.0
130°	493.0	491.7	490.4	489.2	487.9	486.6	485.4	484.1	482.8	482.2	481.3
132.5°	516.4	515.4	514.3	513.3	512.3	511.0	509.8	508.5	507.2	506.6	505.8
135°	539.2	538.1	536.9	535.8	534.6	533.6	532.5	531.5	530.4	529.9	529.0
137.5°	560.4	559.3	558.1	557.0	555.8	554.7	553.5	552.4	551.3	550.7	550.0
140°	580.7	579.7	578.6	577.6	576.6	575.3	574.1	572.8	571.5	570.9	570.4
142.5°	599.4	598.5	597.6	596.7	595.8	594.3	592.8	591.3	589.8	589.0	588.6
145°	616.6	615.8	615.0	614.2	613.4	611.4	609.5	607.5	605.6	604.6	604.7
147.5°	631.8	631.2	630.7	630.1	629.5	627.5	625.5	623.6	621.6	620.6	620.8
150°	646.3	645.6	644.9	644.2	643.5	641.7	639.8	638.0	636.1	635.2	635.6
152.5°	659.2	658.5	657.8	657.1	656.4	654.7	652.9	651.2	649.5	648.6	649.1
155°	670.6	669.9	669.2	668.5	667.8	666.4	665.0	663.7	662.3	661.6	662.1
157.5°	680.9	680.1	679.3	678.5	677.7	676.7	675.6	674.6	673.5	673.0	673.5
160°	689.3	688.6	687.9	687.2	686.5	685.8	685.1	684.4	683.7	683.4	683.7
162.5°	697.5	696.7	695.9	695.1	694.3	693.7	693.1	692.6	692.0	691.7	692.0
165°	703.7	702.9	702.1	701.3	700.5	700.1	699.8	699.4	699.1	698.9	699.3
167.5°	709.4	708.6	707.8	707.0	706.2	705.8	705.5	705.1	704.8	704.6	705.0
170°	713.6	712.8	712.0	711.2	710.4	710.2	709.9	709.7	709.4	709.3	709.6
172.5°	716.7	715.9	715.1	714.3	713.5	713.3	713.0	712.8	712.5	712.4	712.7
175°	718.8	718.0	717.1	716.3	715.5	715.3	715.1	714.8	714.6	714.5	714.9
177.5°	719.3	718.5	717.7	716.9	716.1	716.0	715.8	715.7	715.6	715.5	715.9
180°	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6

TEST NUMBER: P1010156

CATALOG NUMBER: S122RDIP-B675D530UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1464.0	1464.0	1464.0	1464.0
2.5°	1437.6	1434.5	1452.8	1473.2
5°	1408.1	1413.1	1436.5	1465.0
7.5°	1377.5	1388.7	1416.2	1453.8
10°	1334.8	1355.2	1396.9	1435.5
12.5°	1293.1	1320.6	1360.2	1406.0
15°	1246.3	1276.8	1325.7	1380.6
17.5°	1194.4	1229.0	1286.0	1346.0
20°	1139.5	1185.3	1245.3	1310.4
22.5°	1078.4	1133.4	1195.4	1267.7
25°	1019.4	1079.4	1141.5	1224.9
27.5°	961.4	1020.4	1089.6	1174.1
30°	903.4	957.4	1031.6	1122.2
32.5°	841.4	897.3	975.7	1068.3
35°	784.4	840.4	913.6	1005.2
37.5°	723.4	783.4	853.6	948.2
40°	652.1	722.3	790.5	881.1
42.5°	593.1	667.4	733.5	819.0
45°	546.3	616.5	671.5	754.9
47.5°	502.6	559.6	615.5	692.8
50°	460.9	504.6	562.6	631.8
52.5°	418.1	455.8	505.6	570.8
55°	379.5	415.1	459.9	509.7
57.5°	343.9	369.3	414.1	458.8
60°	304.2	330.6	365.2	402.9
62.5°	270.6	291.0	323.5	355.1
65°	235.0	254.3	278.8	308.3
67.5°	202.5	219.8	239.1	262.5
70°	173.0	186.2	200.4	220.8
72.5°	141.4	155.7	168.9	185.2
75°	116.0	122.1	133.3	144.5
77.5°	89.5	97.7	103.8	112.9
80°	64.1	71.2	73.3	80.4
82.5°	42.7	46.8	50.9	52.9
85°	24.4	26.5	30.5	31.5
87.5°	9.2	10.2	12.2	14.2
90°	4.3	3.0	1.8	0.5
92.5°	11.6	12.1	12.5	13.0
95°	22.3	26.1	29.9	33.7
97.5°	32.3	41.8	51.2	60.7
100°	44.4	60.2	76.0	91.8
102.5°	125.3	125.6	125.8	126.0
105°	168.0	164.5	161.1	157.6
107.5°	203.1	200.2	197.3	194.4
110°	237.0	234.5	232.1	229.7

TEST NUMBER: P1010156

CATALOG NUMBER: S122RDIP-B675D530UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	269.1	267.0	265.0	262.9
115°	304.0	302.1	300.1	298.1
117.5°	335.6	333.3	331.0	328.7
120°	368.1	366.4	364.7	363.0
122.5°	397.5	395.7	393.8	392.0
125°	426.0	424.5	423.0	421.5
127.5°	453.4	451.7	450.1	448.5
130°	479.4	477.6	475.7	473.9
132.5°	504.3	502.8	501.3	499.8
135°	527.1	525.3	523.4	521.6
137.5°	548.6	547.2	545.8	544.4
140°	569.5	568.6	567.6	566.7
142.5°	587.8	587.0	586.2	585.4
145°	604.8	604.9	605.0	605.1
147.5°	621.1	621.5	621.8	622.2
150°	636.4	637.2	638.0	638.8
152.5°	650.0	650.9	651.9	652.8
155°	663.2	664.2	665.3	666.3
157.5°	674.4	675.3	676.3	677.2
160°	684.4	685.1	685.8	686.5
162.5°	692.7	693.4	694.1	694.8
165°	700.0	700.7	701.4	702.1
167.5°	705.7	706.4	707.1	707.8
170°	710.3	711.0	711.7	712.4
172.5°	713.4	714.1	714.8	715.5
175°	715.7	716.5	717.3	718.1
177.5°	716.7	717.6	718.4	719.2
180°	716.6	716.6	716.6	716.6

(END OF REPORT)