

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010188

Luminaire Tested: S122RDIP-B675D725UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010188
REPORT IS A COMBINATION OF REPORTS P988540 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B675D725UB27-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5273.0 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010188

CATALOG NUMBER: S122RDIP-B675D725UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1010188

CATALOG NUMBER: S122RDIP-B675D725UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	42	42	42
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	49	48	47	39	38	37
2	90	83	77	73	83	77	72	68	65	61	58	54	52	50	44	43	41	34	33	32
3	83	74	67	61	76	68	62	58	58	54	50	49	46	43	40	38	36	30	29	28
4	76	66	58	53	70	61	55	50	52	47	43	44	40	37	36	34	32	26	25	24
5	70	59	51	46	64	55	48	43	47	42	38	40	36	33	33	30	28	23	22	21
6	65	53	46	40	60	50	43	38	43	38	34	36	32	29	30	28	25	20	19	18
7	60	49	41	36	55	45	39	34	39	34	30	33	29	26	28	25	23	18	17	16
8	56	44	37	32	52	41	35	30	36	31	27	31	27	24	26	23	21	16	15	14
9	52	41	33	29	48	38	32	27	33	28	24	29	25	22	24	21	19	14	13	12
10	49	37	31	26	45	35	29	25	31	26	22	27	23	20	23	20	18	13	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23174	23174	23174	23174
5°	23228	24614	23309	19664
10°	22972	26017	23135	16239
15°	22474	26025	22855	12199
20°	21875	21513	22351	10065
25°	21147	13443	21605	8562
30°	20220	8607	20769	7371
35°	19090	6615	19708	6308
40°	17833	5560	18594	5517
45°	16487	4732	17175	4632
50°	15109	4020	15814	4006
55°	13582	3495	14314	3448
60°	12226	2664	12872	2633
65°	10960	2006	11610	2274
70°	9562	1601	10311	1854
75°	8083	1227	8822	1403
80°	6419	835	6906	919
85°	4450	430	4887	454

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 21199 cd/sqm

TEST NUMBER: P1010188

CATALOG NUMBER: S122RDIP-B675D725UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.9	2.6
10°-20°	387.6	7.4
20°-30°	498.8	9.5
30°-40°	473.3	9.0
40°-50°	405.6	7.7
50°-60°	308.9	5.9
60°-70°	194.8	3.7
70°-80°	97.2	1.8
80°-90°	27.5	0.5
90°-100°	153.4	2.9
100°-110°	540.2	10.2
110°-120°	567.4	10.8
120°-130°	466.8	8.9
130°-140°	375.0	7.1
140°-150°	283.2	5.4
150°-160°	199.1	3.8
160°-170°	117.2	2.2
170°-180°	38.1	0.7
0°-30°	1025.3	19.4
0°-40°	1498.6	28.4
0°-60°	2213.0	42.0
0°-90°	2532.5	48.0
90°-120°	1261.0	23.9
90°-150°	2386.0	45.2
90°-180°	2740.0	52.0
0°-180°	5273.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1464	1464	1464	1464	1464	
5°	1465	1629	1470	1301	1465	139
15°	1381	1838	1404	862	1381	388
25°	1225	981	1251	625	1225	562
35°	1005	483	1038	461	1005	629
45°	755	336	786	329	755	583
55°	510	233	537	230	510	459
65°	308	121	327	137	308	306
75°	144	64	158	73	144	156
85°	32	18	35	19	32	36
90°	1	25	1	25	1	4
95°	26	86	26	86	26	27
105°	92	853	92	853	92	98
115°	163	1122	163	1122	163	161
125°	227	910	227	910	227	202
135°	266	754	266	754	266	206
145°	304	602	304	602	304	191
155°	346	506	346	506	346	159
165°	377	444	377	444	377	106
175°	393	400	393	400	393	37
180°	394	394	394	394	394	

TEST NUMBER: P1010188

CATALOG NUMBER: S122RDIP-B675D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1473.2	1479.3	1482.3	1486.4	1495.6	1501.7	1510.8	1512.8	1511.8	1515.9	1504.7
5°	1465.0	1478.3	1490.5	1500.6	1516.9	1527.1	1538.3	1551.5	1554.6	1569.8	1560.7
7.5°	1453.8	1473.2	1490.5	1510.8	1535.2	1548.5	1565.8	1586.1	1595.3	1613.6	1618.7
10°	1435.5	1463.0	1492.5	1513.9	1547.4	1570.8	1587.1	1619.7	1641.0	1668.5	1664.4
12.5°	1406.0	1441.6	1481.3	1516.9	1560.7	1575.9	1606.4	1640.0	1667.5	1692.9	1715.3
15°	1380.6	1421.3	1465.0	1508.8	1558.6	1587.1	1617.6	1661.4	1690.9	1735.7	1755.0
17.5°	1346.0	1397.9	1449.8	1498.6	1557.6	1590.2	1627.8	1670.5	1714.3	1757.0	1772.3
20°	1310.4	1366.3	1422.3	1488.4	1555.6	1587.1	1625.8	1678.7	1721.4	1755.0	1755.0
22.5°	1267.7	1335.8	1399.9	1463.0	1536.2	1582.0	1621.7	1683.8	1714.3	1721.4	1693.9
25°	1224.9	1293.1	1363.3	1441.6	1525.1	1565.8	1610.5	1668.5	1678.7	1650.2	1579.0
27.5°	1174.1	1250.4	1329.7	1414.2	1501.7	1552.5	1593.2	1631.9	1612.6	1536.2	1425.4
30°	1122.2	1204.6	1294.1	1374.5	1480.3	1527.1	1561.7	1572.9	1511.8	1387.7	1244.3
32.5°	1068.3	1148.6	1243.2	1339.9	1446.7	1491.5	1513.9	1484.4	1372.5	1215.8	1040.8
35°	1005.2	1095.7	1194.4	1295.1	1400.9	1434.5	1447.7	1375.5	1232.1	1029.6	855.6
37.5°	948.2	1038.7	1144.6	1247.3	1350.1	1368.4	1355.2	1242.2	1060.1	859.7	689.8
40°	881.1	977.7	1081.5	1196.4	1280.9	1286.0	1253.4	1106.9	881.1	692.8	588.0
42.5°	819.0	916.7	1020.4	1137.4	1201.5	1184.2	1140.5	948.2	735.6	597.2	512.8
45°	754.9	847.5	959.4	1063.2	1108.9	1068.3	1002.1	797.6	617.6	513.8	448.7
47.5°	692.8	779.3	890.2	989.9	998.1	952.3	873.9	668.4	535.1	451.7	398.8
50°	631.8	718.3	822.0	904.5	896.3	833.2	744.7	580.9	464.9	398.8	355.1
52.5°	570.8	649.1	749.8	814.9	780.3	719.3	631.8	492.4	405.9	347.9	314.4
55°	509.7	583.0	669.4	723.4	668.4	598.2	536.2	422.2	352.0	305.2	279.8
57.5°	458.8	516.8	596.2	628.7	562.6	507.7	453.8	363.2	305.2	271.6	242.1
60°	402.9	455.8	520.9	540.2	472.1	427.3	381.5	307.2	261.5	232.0	212.6
62.5°	355.1	398.8	448.7	448.7	388.6	355.1	320.5	257.4	219.8	196.4	187.2
65°	308.3	339.8	375.4	371.3	320.5	291.0	263.5	212.6	184.1	167.9	158.7
67.5°	262.5	286.9	310.3	296.1	259.4	234.0	208.6	171.9	152.6	141.4	129.2
70°	220.8	240.1	252.3	239.1	202.5	181.1	162.8	138.4	123.1	108.9	101.7
72.5°	185.2	193.3	197.4	181.1	150.6	138.4	125.1	107.8	94.6	87.5	85.5
75°	144.5	151.6	148.5	136.3	110.9	101.7	91.6	79.4	76.3	72.2	70.2
77.5°	112.9	112.9	107.8	96.7	79.4	72.2	68.2	62.1	59.0	58.0	56.0
80°	80.4	79.4	76.3	64.1	53.9	49.9	49.9	45.8	44.8	42.7	42.7
82.5°	52.9	52.9	48.8	38.7	35.6	34.6	33.6	31.5	31.5	30.5	30.5
85°	31.5	29.5	24.4	21.4	20.3	20.3	19.3	18.3	19.3	18.3	18.3
87.5°	14.2	11.2	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
90°	0.8	3.0	6.1	7.6	9.1	10.2	11.4	15.1	20.4	25.0	25.7
92.5°	11.4	15.9	21.9	25.7	31.8	36.0	40.1	60.5	89.3	115.0	116.5
95°	26.5	29.5	37.1	43.9	56.0	65.1	74.2	109.0	174.8	262.6	296.7
97.5°	39.4	43.9	52.2	62.1	75.7	85.9	96.1	140.8	232.3	373.8	483.6
100°	58.3	60.5	67.4	79.5	94.6	105.2	115.8	155.9	248.2	411.7	597.8
102.5°	75.7	77.2	84.0	96.1	112.0	122.6	133.2	169.5	249.0	397.3	601.6
105°	92.3	95.4	100.6	112.0	128.7	139.2	149.8	185.4	252.8	377.6	560.8
107.5°	110.5	112.8	118.1	128.7	145.3	155.9	166.5	201.3	261.1	367.0	522.9
110°	128.7	131.7	136.2	146.1	161.9	172.9	183.9	217.2	271.7	364.0	497.2

TEST NUMBER: P1010188

CATALOG NUMBER: S122RDIP-B675D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	145.3	148.3	153.6	162.7	177.8	189.2	200.5	232.3	283.0	364.8	480.5
115°	162.7	166.5	171.0	180.1	195.2	205.4	215.7	248.2	294.4	367.8	469.2
117.5°	180.9	183.9	188.4	196.8	211.1	221.7	232.3	262.6	306.5	372.3	463.1
120°	197.5	200.5	205.1	211.9	227.0	237.6	248.2	277.7	318.6	376.9	457.8
122.5°	213.4	215.7	220.2	227.8	242.9	253.9	264.9	292.1	329.2	382.2	454.8
125°	227.0	229.3	233.8	242.9	258.1	268.6	279.2	306.5	340.5	387.5	451.0
127.5°	238.4	241.4	247.5	257.3	271.7	282.6	293.6	320.1	351.1	392.8	448.8
130°	248.2	251.2	258.8	269.4	284.5	295.1	305.7	332.2	361.0	398.8	447.2
132.5°	257.3	261.1	269.4	280.8	296.7	307.2	317.8	342.8	370.8	404.9	446.5
135°	266.4	269.4	278.5	289.8	307.2	317.8	328.4	352.7	379.1	409.4	445.7
137.5°	274.7	278.5	287.6	299.7	317.1	327.0	336.8	361.0	386.0	414.0	445.7
140°	284.5	287.6	296.7	308.8	325.4	335.2	345.1	367.8	391.2	417.0	445.0
142.5°	294.4	296.7	305.0	317.1	333.0	342.0	351.1	373.1	395.8	419.2	445.0
145°	304.2	307.2	314.8	326.2	341.3	349.6	358.0	378.4	399.6	420.8	443.5
147.5°	314.8	317.1	324.7	335.2	348.1	355.6	363.2	382.9	401.8	421.5	441.2
150°	325.4	327.7	333.7	343.6	354.9	361.7	368.5	386.0	403.4	420.8	438.9
152.5°	336.0	336.8	342.8	351.1	361.7	367.8	373.8	389.0	404.1	419.2	435.1
155°	345.8	346.6	351.1	359.5	367.8	373.5	379.1	392.0	404.9	417.7	430.6
157.5°	354.2	354.9	358.7	366.3	373.1	378.0	382.9	394.3	404.9	414.7	426.1
160°	362.5	363.2	366.3	372.3	378.4	382.5	386.7	395.8	404.9	412.4	421.5
162.5°	370.8	370.1	373.1	377.6	382.9	386.0	389.0	396.5	404.1	410.2	417.7
165°	376.9	376.1	377.6	382.2	386.0	388.2	390.5	397.3	402.6	407.1	412.4
167.5°	382.2	381.4	382.9	386.0	389.0	390.5	392.0	397.3	401.8	404.1	407.9
170°	387.5	386.0	386.7	389.0	390.5	391.6	392.8	396.5	400.3	401.8	404.1
172.5°	390.5	389.7	389.0	391.2	392.0	392.8	393.5	395.8	398.1	398.8	399.6
175°	392.8	392.0	391.2	392.8	392.8	393.2	393.5	395.0	396.5	395.8	396.5
177.5°	394.3	392.8	392.0	393.5	393.5	393.5	393.5	394.3	395.8	394.3	393.5
180°	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5

TEST NUMBER: P1010188

CATALOG NUMBER: S122RDIP-B675D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1515.9	1517.9	1521.0	1535.2	1537.3	1541.3	1539.3	1539.3	1540.3	1538.3	1539.3
5°	1581.0	1584.1	1599.3	1616.6	1620.7	1616.6	1621.7	1628.8	1628.8	1628.8	1626.8
7.5°	1642.1	1653.2	1670.5	1696.0	1701.1	1706.2	1715.3	1709.2	1711.2	1720.4	1717.3
10°	1701.1	1717.3	1736.7	1758.0	1769.2	1776.4	1780.4	1789.6	1810.9	1786.5	1795.7
12.5°	1757.0	1780.4	1800.8	1824.2	1832.3	1841.5	1844.5	1852.7	1852.7	1851.6	1858.8
15°	1793.6	1815.0	1833.3	1848.6	1850.6	1848.6	1846.6	1847.6	1850.6	1838.4	1845.5
17.5°	1801.8	1803.8	1809.9	1803.8	1804.8	1783.5	1771.3	1768.2	1739.7	1740.7	1764.1
20°	1762.1	1727.5	1718.4	1684.8	1664.4	1609.5	1607.5	1592.2	1532.2	1550.5	1546.4
22.5°	1653.2	1594.2	1515.9	1477.2	1457.9	1399.9	1355.2	1323.6	1302.3	1280.9	1271.7
25°	1509.8	1414.2	1303.3	1227.0	1215.8	1161.9	1079.4	1040.8	995.0	980.8	1005.2
27.5°	1324.6	1200.5	1075.4	958.4	937.0	888.2	846.5	819.0	766.1	763.0	765.1
30°	1073.3	948.2	843.4	767.1	714.2	691.8	664.4	644.0	622.6	630.8	632.8
32.5°	882.1	763.0	665.4	624.7	600.3	586.0	562.6	549.4	540.2	537.2	536.2
35°	701.0	621.6	577.9	538.2	524.0	513.8	496.5	490.4	482.2	483.3	483.3
37.5°	600.3	534.1	501.6	481.2	468.0	462.9	451.7	445.6	440.5	438.5	441.5
40°	517.8	472.1	451.7	433.4	422.2	420.2	414.1	407.0	400.8	401.9	404.9
42.5°	457.8	431.4	407.0	392.7	384.6	381.5	376.4	371.3	371.3	368.3	367.3
45°	410.0	388.6	368.3	355.1	350.0	345.9	339.8	338.8	334.7	335.7	336.8
47.5°	367.3	350.0	334.7	321.5	316.4	315.4	309.3	305.2	305.2	304.2	303.2
50°	328.6	311.3	298.1	291.0	283.9	281.8	280.8	279.8	277.7	277.7	278.8
52.5°	297.1	279.8	269.6	263.5	259.4	257.4	257.4	256.4	256.4	256.4	255.4
55°	262.5	248.2	240.1	238.1	236.0	235.0	234.0	232.0	230.9	233.0	230.9
57.5°	229.9	224.8	217.7	215.7	210.6	210.6	207.5	205.5	203.5	205.5	205.5
60°	204.5	197.4	193.3	187.2	183.1	179.1	174.0	173.0	170.9	169.9	168.9
62.5°	178.0	171.9	161.8	152.6	146.5	142.4	140.4	139.4	139.4	138.4	138.4
65°	148.5	134.3	129.2	126.2	125.1	124.1	122.1	121.1	122.1	121.1	122.1
67.5°	116.0	113.9	110.9	108.9	107.8	106.8	106.8	105.8	105.8	105.8	105.8
70°	100.7	95.6	94.6	92.6	92.6	91.6	91.6	91.6	91.6	90.5	92.6
72.5°	83.4	80.4	79.4	78.3	78.3	78.3	77.3	77.3	77.3	76.3	77.3
75°	68.2	67.1	65.1	65.1	64.1	65.1	64.1	64.1	63.1	64.1	64.1
77.5°	54.9	53.9	52.9	52.9	51.9	51.9	51.9	51.9	51.9	51.9	52.9
80°	41.7	40.7	39.7	40.7	39.7	40.7	39.7	39.7	40.7	39.7	39.7
82.5°	30.5	29.5	29.5	28.5	28.5	28.5	28.5	28.5	28.5	28.5	28.5
85°	18.3	17.3	17.3	18.3	17.3	18.3	17.3	17.3	17.3	18.3	18.3
87.5°	8.1	9.2	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	9.2
90°	25.0	24.2	22.7	24.2	24.6	25.0	25.0	25.0	25.0	25.0	25.0
92.5°	97.6	76.4	65.1	56.8	53.8	50.7	49.9	46.9	47.7	46.2	47.7
95°	259.6	198.3	152.1	120.3	112.0	103.7	93.8	87.8	85.5	86.3	85.5
97.5°	487.4	405.6	323.9	247.5	224.8	202.1	172.5	157.4	149.1	144.5	149.1
100°	706.8	690.9	597.1	493.4	447.6	401.8	339.0	306.5	284.5	270.9	284.5
102.5°	788.5	877.8	874.8	806.0	756.8	707.6	638.0	576.7	547.9	528.2	547.9
105°	762.1	919.5	1005.0	1014.8	1002.3	989.8	942.9	896.0	863.5	852.9	863.5
107.5°	706.1	874.8	1002.0	1076.1	1091.2	1106.4	1105.6	1098.8	1089.0	1071.6	1089.0
110°	653.8	813.5	949.0	1045.9	1076.9	1107.9	1140.4	1154.8	1161.6	1160.9	1161.6

TEST NUMBER: P1010188

CATALOG NUMBER: S122RDIP-B675D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	617.5	757.5	886.2	991.4	1028.1	1064.8	1113.2	1139.7	1154.1	1159.4	1154.1
115°	588.8	713.6	830.2	929.3	968.3	1007.3	1061.0	1095.8	1115.5	1122.3	1115.5
117.5°	569.1	677.3	781.7	874.1	911.2	948.2	1003.5	1040.6	1061.0	1066.3	1061.0
120°	554.0	651.6	745.4	825.6	860.0	894.5	947.5	983.0	1005.0	1012.6	1005.0
122.5°	541.1	631.1	715.1	790.1	820.4	850.6	896.8	931.6	950.5	956.6	950.5
125°	529.0	611.5	689.4	756.0	784.4	812.8	856.7	885.4	904.3	910.4	904.3
127.5°	517.6	591.8	663.7	727.3	753.8	780.2	818.8	846.1	862.7	867.3	862.7
130°	506.3	572.9	638.0	697.7	722.7	747.7	784.8	810.5	825.6	831.7	825.6
132.5°	497.2	554.7	613.7	667.5	690.6	713.6	750.0	775.7	789.3	794.6	789.3
135°	488.9	538.1	588.0	638.0	659.2	680.3	712.9	737.8	751.5	754.5	751.5
137.5°	482.8	524.4	567.6	608.4	627.3	646.3	677.3	699.3	711.4	715.9	711.4
140°	477.5	511.6	547.9	582.7	599.4	616.0	640.2	659.9	671.3	675.8	671.3
142.5°	472.2	501.0	530.5	559.2	572.4	585.7	608.4	625.8	635.7	635.7	635.7
145°	467.7	491.1	516.1	539.6	550.6	561.5	579.7	592.5	600.1	602.4	600.1
147.5°	463.1	483.6	504.0	522.9	531.2	539.6	555.5	566.1	571.4	572.9	571.4
150°	457.1	475.2	491.9	507.8	514.6	521.4	532.8	541.8	546.4	547.1	546.4
152.5°	451.8	466.9	482.1	494.9	500.6	506.3	514.6	522.2	525.2	525.2	525.2
155°	445.0	459.4	471.5	482.8	487.0	491.1	499.5	504.8	507.8	506.3	507.8
157.5°	438.9	450.3	460.9	470.7	474.1	477.5	483.6	488.1	489.6	489.6	489.6
160°	432.1	442.0	450.3	458.6	461.2	463.9	469.2	473.0	473.7	473.7	473.7
162.5°	426.1	433.6	440.4	447.2	449.1	451.0	456.3	458.6	459.4	458.6	459.4
165°	419.2	425.3	430.6	435.9	437.4	438.9	442.0	445.0	445.0	444.2	445.0
167.5°	412.4	417.0	421.5	425.3	426.8	428.3	429.8	431.4	431.4	430.6	431.4
170°	407.1	410.9	413.2	416.2	417.0	417.7	418.5	420.8	420.0	418.5	420.0
172.5°	401.8	404.1	405.6	407.9	408.3	408.7	409.4	410.2	409.4	408.7	409.4
175°	397.3	399.6	400.3	401.1	401.5	401.8	401.8	402.6	401.8	400.3	401.8
177.5°	394.3	395.8	395.8	396.5	396.5	396.5	396.5	396.5	395.8	394.3	395.8
180°	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5

TEST NUMBER: P1010188

CATALOG NUMBER: S122RDIP-B675D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1543.4	1536.2	1534.2	1536.2	1534.2	1535.2	1528.1	1501.7	1508.8	1497.6	1503.7
5°	1630.9	1624.8	1611.5	1609.5	1607.5	1605.4	1595.3	1571.9	1562.7	1547.4	1546.4
7.5°	1714.3	1714.3	1704.1	1697.0	1687.8	1680.7	1667.5	1632.9	1618.7	1600.3	1590.2
10°	1796.7	1770.2	1781.4	1774.3	1751.9	1747.9	1723.4	1703.1	1675.6	1657.3	1641.0
12.5°	1855.7	1847.6	1837.4	1831.3	1825.2	1812.0	1795.7	1743.8	1729.6	1692.9	1674.6
15°	1853.7	1848.6	1851.6	1851.6	1849.6	1846.6	1833.3	1795.7	1771.3	1735.7	1704.1
17.5°	1754.0	1767.2	1780.4	1789.6	1809.9	1819.1	1831.3	1808.9	1793.6	1763.1	1729.6
20°	1580.0	1612.6	1651.2	1659.4	1677.7	1731.6	1756.0	1775.3	1781.4	1771.3	1743.8
22.5°	1337.9	1365.3	1458.9	1456.9	1483.3	1547.4	1618.7	1676.6	1722.4	1747.9	1737.7
25°	1047.9	1086.6	1136.4	1174.1	1260.5	1356.2	1444.7	1537.3	1616.6	1686.8	1704.1
27.5°	792.5	843.4	883.1	932.9	976.7	1089.6	1203.6	1348.0	1440.6	1573.9	1643.1
30°	641.0	664.4	704.0	727.4	748.8	835.3	964.5	1106.9	1269.7	1423.3	1542.4
32.5°	547.4	563.6	593.1	603.3	625.7	683.7	765.1	895.3	1063.2	1249.3	1406.0
35°	491.4	508.7	514.8	524.0	542.3	578.9	634.8	729.5	881.1	1063.2	1250.4
37.5°	443.6	452.7	470.0	476.1	482.2	509.7	547.4	613.5	714.2	863.8	1071.3
40°	410.0	415.1	424.2	429.3	433.4	452.7	486.3	531.1	605.3	719.3	910.6
42.5°	374.4	380.5	386.6	392.7	397.8	413.1	433.4	476.1	526.0	612.5	750.8
45°	339.8	343.9	351.0	355.1	362.2	374.4	392.7	422.2	467.0	521.9	633.8
47.5°	308.3	313.4	316.4	321.5	326.6	339.8	357.1	376.4	413.1	467.0	548.4
50°	279.8	285.9	290.0	291.0	295.0	307.2	321.5	342.9	366.3	408.0	479.2
52.5°	259.4	260.5	263.5	267.6	266.6	273.7	286.9	303.2	327.6	361.2	413.1
55°	236.0	239.1	241.1	242.1	242.1	248.2	255.4	270.6	290.0	317.4	361.2
57.5°	206.5	209.6	215.7	217.7	220.8	223.8	226.9	237.1	253.3	279.8	315.4
60°	176.0	178.0	184.1	188.2	190.3	198.4	202.5	210.6	219.8	239.1	272.7
62.5°	141.4	143.5	146.5	150.6	154.6	166.9	177.0	185.2	192.3	205.5	233.0
65°	123.1	124.1	126.2	127.2	128.2	133.3	142.4	153.6	166.9	177.0	193.3
67.5°	106.8	107.8	108.9	110.9	111.9	112.9	117.0	120.1	133.3	147.5	159.7
70°	91.6	93.6	94.6	94.6	95.6	97.7	99.7	103.8	107.8	115.0	130.2
72.5°	77.3	78.3	80.4	80.4	80.4	82.4	84.4	86.5	88.5	92.6	98.7
75°	64.1	66.1	66.1	66.1	67.1	67.1	69.2	71.2	73.3	76.3	78.3
77.5°	52.9	52.9	52.9	52.9	53.9	53.9	54.9	57.0	58.0	59.0	61.0
80°	39.7	40.7	40.7	40.7	41.7	41.7	41.7	43.7	44.8	44.8	46.8
82.5°	29.5	29.5	29.5	30.5	29.5	30.5	30.5	31.5	30.5	31.5	32.6
85°	18.3	18.3	18.3	19.3	19.3	19.3	19.3	19.3	19.3	19.3	20.3
87.5°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	10.2	9.2	9.2
90°	25.0	25.0	25.0	24.6	24.2	22.7	24.2	25.0	25.7	25.0	20.4
92.5°	46.9	49.9	50.7	53.8	56.8	65.1	76.4	97.6	116.5	115.0	89.3
95°	87.8	93.8	103.7	112.0	120.3	152.1	198.3	259.6	296.7	262.6	174.8
97.5°	157.4	172.5	202.1	224.8	247.5	323.9	405.6	487.4	483.6	373.8	232.3
100°	306.5	339.0	401.8	447.6	493.4	597.1	690.9	706.8	597.8	411.7	248.2
102.5°	576.7	638.0	707.6	756.8	806.0	874.8	877.8	788.5	601.6	397.3	249.0
105°	896.0	942.9	989.8	1002.3	1014.8	1005.0	919.5	762.1	560.8	377.6	252.8
107.5°	1098.8	1105.6	1106.4	1091.2	1076.1	1002.0	874.8	706.1	522.9	367.0	261.1
110°	1154.8	1140.4	1107.9	1076.9	1045.9	949.0	813.5	653.8	497.2	364.0	271.7

TEST NUMBER: P1010188

CATALOG NUMBER: S122RDIP-B675D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1139.7	1113.2	1064.8	1028.1	991.4	886.2	757.5	617.5	480.5	364.8	283.0
115°	1095.8	1061.0	1007.3	968.3	929.3	830.2	713.6	588.8	469.2	367.8	294.4
117.5°	1040.6	1003.5	948.2	911.2	874.1	781.7	677.3	569.1	463.1	372.3	306.5
120°	983.0	947.5	894.5	860.0	825.6	745.4	651.6	554.0	457.8	376.9	318.6
122.5°	931.6	896.8	850.6	820.4	790.1	715.1	631.1	541.1	454.8	382.2	329.2
125°	885.4	856.7	812.8	784.4	756.0	689.4	611.5	529.0	451.0	387.5	340.5
127.5°	846.1	818.8	780.2	753.8	727.3	663.7	591.8	517.6	448.8	392.8	351.1
130°	810.5	784.8	747.7	722.7	697.7	638.0	572.9	506.3	447.2	398.8	361.0
132.5°	775.7	750.0	713.6	690.6	667.5	613.7	554.7	497.2	446.5	404.9	370.8
135°	737.8	712.9	680.3	659.2	638.0	588.0	538.1	488.9	445.7	409.4	379.1
137.5°	699.3	677.3	646.3	627.3	608.4	567.6	524.4	482.8	445.7	414.0	386.0
140°	659.9	640.2	616.0	599.4	582.7	547.9	511.6	477.5	445.0	417.0	391.2
142.5°	625.8	608.4	585.7	572.4	559.2	530.5	501.0	472.2	445.0	419.2	395.8
145°	592.5	579.7	561.5	550.6	539.6	516.1	491.1	467.7	443.5	420.8	399.6
147.5°	566.1	555.5	539.6	531.2	522.9	504.0	483.6	463.1	441.2	421.5	401.8
150°	541.8	532.8	521.4	514.6	507.8	491.9	475.2	457.1	438.9	420.8	403.4
152.5°	522.2	514.6	506.3	500.6	494.9	482.1	466.9	451.8	435.1	419.2	404.1
155°	504.8	499.5	491.1	487.0	482.8	471.5	459.4	445.0	430.6	417.7	404.9
157.5°	488.1	483.6	477.5	474.1	470.7	460.9	450.3	438.9	426.1	414.7	404.9
160°	473.0	469.2	463.9	461.2	458.6	450.3	442.0	432.1	421.5	412.4	404.9
162.5°	458.6	456.3	451.0	449.1	447.2	440.4	433.6	426.1	417.7	410.2	404.1
165°	445.0	442.0	438.9	437.4	435.9	430.6	425.3	419.2	412.4	407.1	402.6
167.5°	431.4	429.8	428.3	426.8	425.3	421.5	417.0	412.4	407.9	404.1	401.8
170°	420.8	418.5	417.7	417.0	416.2	413.2	410.9	407.1	404.1	401.8	400.3
172.5°	410.2	409.4	408.7	408.3	407.9	405.6	404.1	401.8	399.6	398.8	398.1
175°	402.6	401.8	401.8	401.5	401.1	400.3	399.6	397.3	396.5	395.8	396.5
177.5°	396.5	396.5	396.5	396.5	396.5	395.8	395.8	394.3	393.5	394.3	395.8
180°	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5

TEST NUMBER: P1010188

CATALOG NUMBER: S122RDIP-B675D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1494.5	1489.4	1489.4	1486.4	1486.4	1470.1	1470.1	1475.2	1469.1	1462.0	1451.8
5°	1533.2	1522.0	1519.0	1514.9	1501.7	1481.3	1473.2	1470.1	1457.9	1442.7	1425.4
7.5°	1569.8	1551.5	1542.4	1533.2	1515.9	1487.4	1471.1	1459.9	1441.6	1418.2	1395.9
10°	1605.4	1582.0	1558.6	1547.4	1523.0	1487.4	1464.0	1445.7	1419.3	1387.7	1356.2
12.5°	1638.0	1589.2	1585.1	1562.7	1527.1	1486.4	1450.8	1424.3	1390.8	1354.1	1317.5
15°	1666.5	1616.6	1592.2	1571.9	1525.1	1474.2	1436.5	1404.0	1359.2	1317.5	1272.7
17.5°	1680.7	1626.8	1610.5	1576.9	1529.1	1463.0	1412.1	1372.5	1323.6	1273.8	1222.9
20°	1695.0	1631.9	1605.4	1582.0	1516.9	1441.6	1384.7	1338.9	1285.0	1225.9	1170.0
22.5°	1702.1	1631.9	1600.3	1567.8	1504.7	1418.2	1351.1	1297.2	1234.1	1174.1	1106.9
25°	1689.9	1625.8	1588.1	1554.6	1483.3	1389.7	1312.4	1251.4	1184.2	1116.1	1047.9
27.5°	1659.4	1611.5	1567.8	1533.2	1453.8	1353.1	1271.7	1202.5	1133.4	1057.1	987.9
30°	1602.4	1581.0	1546.4	1507.8	1421.3	1320.6	1223.9	1152.7	1076.4	1000.1	927.9
32.5°	1513.9	1532.2	1509.8	1476.2	1382.6	1275.8	1173.0	1100.8	1017.4	935.0	868.8
35°	1406.0	1471.1	1458.9	1435.5	1341.9	1228.0	1125.2	1037.7	954.3	870.9	804.8
37.5°	1288.0	1386.7	1396.9	1382.6	1295.1	1179.1	1066.2	980.8	895.3	810.9	743.7
40°	1126.2	1277.8	1310.4	1316.5	1246.3	1120.1	1002.1	918.7	834.3	751.8	670.5
42.5°	977.7	1169.0	1209.7	1235.1	1184.2	1062.1	943.1	850.5	767.1	692.8	611.4
45°	838.3	1037.7	1103.9	1136.4	1114.0	996.0	872.9	786.4	710.1	642.0	563.6
47.5°	694.9	895.3	987.9	1039.8	1039.8	928.9	805.8	720.3	647.1	589.1	519.9
50°	599.2	766.1	861.7	929.9	948.2	860.7	744.7	661.3	592.1	529.0	476.1
52.5°	510.7	660.3	739.6	810.9	863.8	787.5	676.6	601.3	533.1	474.1	432.4
55°	441.5	553.5	625.7	704.0	763.0	713.2	610.4	537.2	478.2	429.3	393.7
57.5°	375.4	473.1	532.1	601.3	664.4	626.7	544.3	481.2	429.3	386.6	355.1
60°	319.5	398.8	444.6	498.5	576.9	550.4	482.2	424.2	382.5	343.9	317.4
62.5°	271.6	334.7	373.4	412.0	483.3	471.0	418.1	373.4	337.8	305.2	282.8
65°	222.8	274.7	305.2	338.8	395.8	400.8	358.1	326.6	294.0	265.5	245.2
67.5°	180.1	220.8	248.2	276.7	322.5	336.8	307.2	280.8	253.3	229.9	211.6
70°	145.5	174.0	194.3	216.7	254.3	271.6	256.4	238.1	215.7	196.4	180.1
72.5°	115.0	133.3	145.5	162.8	193.3	210.6	209.6	193.3	177.0	163.8	150.6
75°	84.4	98.7	108.9	120.1	144.5	160.7	164.8	157.7	141.4	131.2	121.1
77.5°	64.1	72.2	77.3	85.5	102.8	117.0	123.1	121.1	109.9	101.7	94.6
80°	48.8	50.9	52.9	56.0	70.2	83.4	87.5	86.5	80.4	77.3	69.2
82.5°	34.6	35.6	36.6	37.6	42.7	53.9	58.0	60.0	54.9	51.9	44.8
85°	20.3	21.4	21.4	23.4	24.4	27.5	34.6	34.6	33.6	29.5	28.5
87.5°	10.2	10.2	9.2	9.2	10.2	11.2	13.2	15.3	13.2	12.2	11.2
90°	15.1	11.4	10.2	9.1	7.6	6.1	3.0	0.8	3.0	6.1	7.6
92.5°	60.5	40.1	36.0	31.8	25.7	21.9	15.9	11.4	15.9	21.9	25.7
95°	109.0	74.2	65.1	56.0	43.9	37.1	29.5	26.5	29.5	37.1	43.9
97.5°	140.8	96.1	85.9	75.7	62.1	52.2	43.9	39.4	43.9	52.2	62.1
100°	155.9	115.8	105.2	94.6	79.5	67.4	60.5	58.3	60.5	67.4	79.5
102.5°	169.5	133.2	122.6	112.0	96.1	84.0	77.2	75.7	77.2	84.0	96.1
105°	185.4	149.8	139.2	128.7	112.0	100.6	95.4	92.3	95.4	100.6	112.0
107.5°	201.3	166.5	155.9	145.3	128.7	118.1	112.8	110.5	112.8	118.1	128.7
110°	217.2	183.9	172.9	161.9	146.1	136.2	131.7	128.7	131.7	136.2	146.1

TEST NUMBER: P1010188

CATALOG NUMBER: S122RDIP-B675D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	232.3	200.5	189.2	177.8	162.7	153.6	148.3	145.3	148.3	153.6	162.7
115°	248.2	215.7	205.4	195.2	180.1	171.0	166.5	162.7	166.5	171.0	180.1
117.5°	262.6	232.3	221.7	211.1	196.8	188.4	183.9	180.9	183.9	188.4	196.8
120°	277.7	248.2	237.6	227.0	211.9	205.1	200.5	197.5	200.5	205.1	211.9
122.5°	292.1	264.9	253.9	242.9	227.8	220.2	215.7	213.4	215.7	220.2	227.8
125°	306.5	279.2	268.6	258.1	242.9	233.8	229.3	227.0	229.3	233.8	242.9
127.5°	320.1	293.6	282.6	271.7	257.3	247.5	241.4	238.4	241.4	247.5	257.3
130°	332.2	305.7	295.1	284.5	269.4	258.8	251.2	248.2	251.2	258.8	269.4
132.5°	342.8	317.8	307.2	296.7	280.8	269.4	261.1	257.3	261.1	269.4	280.8
135°	352.7	328.4	317.8	307.2	289.8	278.5	269.4	266.4	269.4	278.5	289.8
137.5°	361.0	336.8	327.0	317.1	299.7	287.6	278.5	274.7	278.5	287.6	299.7
140°	367.8	345.1	335.2	325.4	308.8	296.7	287.6	284.5	287.6	296.7	308.8
142.5°	373.1	351.1	342.0	333.0	317.1	305.0	296.7	294.4	296.7	305.0	317.1
145°	378.4	358.0	349.6	341.3	326.2	314.8	307.2	304.2	307.2	314.8	326.2
147.5°	382.9	363.2	355.6	348.1	335.2	324.7	317.1	314.8	317.1	324.7	335.2
150°	386.0	368.5	361.7	354.9	343.6	333.7	327.7	325.4	327.7	333.7	343.6
152.5°	389.0	373.8	367.8	361.7	351.1	342.8	336.8	336.0	336.8	342.8	351.1
155°	392.0	379.1	373.5	367.8	359.5	351.1	346.6	345.8	346.6	351.1	359.5
157.5°	394.3	382.9	378.0	373.1	366.3	358.7	354.9	354.2	354.9	358.7	366.3
160°	395.8	386.7	382.5	378.4	372.3	366.3	363.2	362.5	363.2	366.3	372.3
162.5°	396.5	389.0	386.0	382.9	377.6	373.1	370.1	370.8	370.1	373.1	377.6
165°	397.3	390.5	388.2	386.0	382.2	377.6	376.1	376.9	376.1	377.6	382.2
167.5°	397.3	392.0	390.5	389.0	386.0	382.9	381.4	382.2	381.4	382.9	386.0
170°	396.5	392.8	391.6	390.5	389.0	386.7	386.0	387.5	386.0	386.7	389.0
172.5°	395.8	393.5	392.8	392.0	391.2	389.0	389.7	390.5	389.7	389.0	391.2
175°	395.0	393.5	393.2	392.8	392.8	391.2	392.0	392.8	392.0	391.2	392.8
177.5°	394.3	393.5	393.5	393.5	393.5	392.0	392.8	394.3	392.8	392.0	393.5
180°	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5

TEST NUMBER: P1010188

CATALOG NUMBER: S122RDIP-B675D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1447.7	1448.8	1451.8	1442.7	1428.4	1422.3	1404.0	1400.9	1397.9	1397.9	1400.9
5°	1415.2	1411.1	1412.1	1394.8	1374.5	1362.3	1336.8	1340.9	1327.7	1319.5	1321.6
7.5°	1379.6	1368.4	1367.4	1345.0	1319.5	1297.2	1270.7	1264.6	1252.4	1238.2	1232.1
10°	1334.8	1326.7	1311.4	1286.0	1253.4	1235.1	1199.5	1178.1	1175.1	1153.7	1145.6
12.5°	1289.0	1274.8	1259.5	1223.9	1187.3	1157.8	1131.3	1107.9	1091.7	1073.3	1061.1
15°	1236.1	1218.8	1201.5	1163.9	1121.2	1091.7	1052.0	1017.4	969.6	931.9	910.6
17.5°	1178.1	1158.8	1135.4	1093.7	1052.0	1011.3	938.0	897.3	863.8	841.4	828.2
20°	1118.1	1096.7	1073.3	1031.6	959.4	888.2	847.5	815.9	795.6	773.2	756.9
22.5°	1055.0	1032.6	1007.2	942.1	865.8	815.9	784.4	754.9	725.4	713.2	705.0
25°	996.0	975.7	943.1	854.6	794.6	748.8	713.2	693.9	678.6	662.3	647.1
27.5°	935.0	897.3	851.6	777.3	739.6	692.8	667.4	653.2	626.7	615.5	608.4
30°	861.7	820.0	776.3	723.4	679.6	647.1	623.7	600.3	585.0	573.8	561.6
32.5°	787.5	747.8	720.3	665.4	632.8	599.2	576.9	562.6	540.2	533.1	528.0
35°	723.4	689.8	665.4	620.6	590.1	559.6	543.3	521.9	507.7	494.4	486.3
37.5°	660.3	642.0	616.5	578.9	546.3	521.9	499.5	492.4	473.1	466.0	457.8
40°	616.5	589.1	567.7	535.1	507.7	481.2	467.0	450.7	437.5	426.3	423.2
42.5°	563.6	543.3	531.1	495.5	467.0	451.7	434.4	416.1	405.9	396.8	385.6
45°	524.0	505.6	488.3	459.9	434.4	415.1	399.8	387.6	370.3	366.3	349.0
47.5°	482.2	463.9	450.7	422.2	398.8	380.5	369.3	353.0	338.8	329.6	321.5
50°	440.5	425.3	413.1	388.6	368.3	349.0	333.7	317.4	311.3	296.1	291.0
52.5°	400.8	390.7	377.4	354.0	333.7	317.4	301.1	287.9	278.8	270.6	264.5
55°	367.3	351.0	344.9	319.5	302.2	284.9	270.6	262.5	251.3	246.2	241.1
57.5°	329.6	320.5	310.3	291.0	271.6	255.4	245.2	233.0	226.9	220.8	216.7
60°	297.1	283.9	275.7	259.4	242.1	226.9	217.7	208.6	200.4	195.3	187.2
62.5°	259.4	249.3	244.2	226.9	212.6	198.4	190.3	181.1	175.0	165.8	155.7
65°	226.9	218.7	212.6	198.4	185.2	171.9	163.8	152.6	144.5	139.4	138.4
67.5°	198.4	192.3	183.1	169.9	156.7	146.5	137.3	128.2	127.2	125.1	125.1
70°	166.9	160.7	155.7	141.4	130.2	119.0	117.0	113.9	110.9	109.9	107.8
72.5°	139.4	134.3	128.2	116.0	104.8	101.7	99.7	97.7	94.6	93.6	92.6
75°	112.9	105.8	101.7	90.5	87.5	85.5	83.4	80.4	78.3	77.3	75.3
77.5°	86.5	79.4	79.4	73.3	71.2	68.2	66.1	64.1	63.1	61.0	61.0
80°	61.0	61.0	59.0	56.0	52.9	51.9	48.8	47.8	46.8	47.8	45.8
82.5°	44.8	40.7	40.7	38.7	36.6	35.6	33.6	33.6	32.6	32.6	32.6
85°	25.4	25.4	24.4	22.4	21.4	21.4	20.3	20.3	19.3	19.3	18.3
87.5°	10.2	9.2	10.2	9.2	9.2	8.1	8.1	8.1	7.1	8.1	7.1
90°	9.1	10.2	11.4	15.1	20.4	25.0	25.7	25.0	24.2	22.7	24.2
92.5°	31.8	36.0	40.1	60.5	89.3	115.0	116.5	97.6	76.4	65.1	56.8
95°	56.0	65.1	74.2	109.0	174.8	262.6	296.7	259.6	198.3	152.1	120.3
97.5°	75.7	85.9	96.1	140.8	232.3	373.8	483.6	487.4	405.6	323.9	247.5
100°	94.6	105.2	115.8	155.9	248.2	411.7	597.8	706.8	690.9	597.1	493.4
102.5°	112.0	122.6	133.2	169.5	249.0	397.3	601.6	788.5	877.8	874.8	806.0
105°	128.7	139.2	149.8	185.4	252.8	377.6	560.8	762.1	919.5	1005.0	1014.8
107.5°	145.3	155.9	166.5	201.3	261.1	367.0	522.9	706.1	874.8	1002.0	1076.1
110°	161.9	172.9	183.9	217.2	271.7	364.0	497.2	653.8	813.5	949.0	1045.9

TEST NUMBER: P1010188

CATALOG NUMBER: S122RDIP-B675D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	177.8	189.2	200.5	232.3	283.0	364.8	480.5	617.5	757.5	886.2	991.4
115°	195.2	205.4	215.7	248.2	294.4	367.8	469.2	588.8	713.6	830.2	929.3
117.5°	211.1	221.7	232.3	262.6	306.5	372.3	463.1	569.1	677.3	781.7	874.1
120°	227.0	237.6	248.2	277.7	318.6	376.9	457.8	554.0	651.6	745.4	825.6
122.5°	242.9	253.9	264.9	292.1	329.2	382.2	454.8	541.1	631.1	715.1	790.1
125°	258.1	268.6	279.2	306.5	340.5	387.5	451.0	529.0	611.5	689.4	756.0
127.5°	271.7	282.6	293.6	320.1	351.1	392.8	448.8	517.6	591.8	663.7	727.3
130°	284.5	295.1	305.7	332.2	361.0	398.8	447.2	506.3	572.9	638.0	697.7
132.5°	296.7	307.2	317.8	342.8	370.8	404.9	446.5	497.2	554.7	613.7	667.5
135°	307.2	317.8	328.4	352.7	379.1	409.4	445.7	488.9	538.1	588.0	638.0
137.5°	317.1	327.0	336.8	361.0	386.0	414.0	445.7	482.8	524.4	567.6	608.4
140°	325.4	335.2	345.1	367.8	391.2	417.0	445.0	477.5	511.6	547.9	582.7
142.5°	333.0	342.0	351.1	373.1	395.8	419.2	445.0	472.2	501.0	530.5	559.2
145°	341.3	349.6	358.0	378.4	399.6	420.8	443.5	467.7	491.1	516.1	539.6
147.5°	348.1	355.6	363.2	382.9	401.8	421.5	441.2	463.1	483.6	504.0	522.9
150°	354.9	361.7	368.5	386.0	403.4	420.8	438.9	457.1	475.2	491.9	507.8
152.5°	361.7	367.8	373.8	389.0	404.1	419.2	435.1	451.8	466.9	482.1	494.9
155°	367.8	373.5	379.1	392.0	404.9	417.7	430.6	445.0	459.4	471.5	482.8
157.5°	373.1	378.0	382.9	394.3	404.9	414.7	426.1	438.9	450.3	460.9	470.7
160°	378.4	382.5	386.7	395.8	404.9	412.4	421.5	432.1	442.0	450.3	458.6
162.5°	382.9	386.0	389.0	396.5	404.1	410.2	417.7	426.1	433.6	440.4	447.2
165°	386.0	388.2	390.5	397.3	402.6	407.1	412.4	419.2	425.3	430.6	435.9
167.5°	389.0	390.5	392.0	397.3	401.8	404.1	407.9	412.4	417.0	421.5	425.3
170°	390.5	391.6	392.8	396.5	400.3	401.8	404.1	407.1	410.9	413.2	416.2
172.5°	392.0	392.8	393.5	395.8	398.1	398.8	399.6	401.8	404.1	405.6	407.9
175°	392.8	393.2	393.5	395.0	396.5	395.8	396.5	397.3	399.6	400.3	401.1
177.5°	393.5	393.5	393.5	394.3	395.8	394.3	393.5	394.3	395.8	395.8	396.5
180°	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5

TEST NUMBER: P1010188

CATALOG NUMBER: S122RDIP-B675D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1400.9	1398.9	1392.8	1394.8	1391.8	1391.8	1389.7	1389.7	1389.7	1394.8	1391.8
5°	1324.6	1317.5	1310.4	1307.3	1304.3	1301.2	1301.2	1300.2	1309.4	1307.3	1315.5
7.5°	1230.0	1228.0	1213.7	1213.7	1208.7	1206.6	1211.7	1212.7	1213.7	1215.8	1220.9
10°	1145.6	1140.5	1120.1	1122.2	1119.1	1115.1	1118.1	1116.1	1123.2	1125.2	1123.2
12.5°	1045.9	1036.7	1014.3	1003.1	990.9	981.8	993.0	984.8	1013.3	1021.5	1043.8
15°	913.6	896.3	881.1	881.1	869.9	861.7	866.8	876.0	882.1	891.2	895.3
17.5°	825.1	818.0	805.8	798.6	795.6	792.5	792.5	796.6	809.8	808.8	817.0
20°	749.8	745.7	739.6	730.5	727.4	725.4	725.4	725.4	734.6	742.7	747.8
22.5°	697.9	694.9	690.8	678.6	672.5	670.5	675.5	678.6	685.7	691.8	696.9
25°	646.0	638.9	631.8	627.7	624.7	624.7	626.7	627.7	630.8	633.8	639.9
27.5°	603.3	598.2	588.0	576.9	576.9	573.8	575.8	577.9	585.0	595.2	600.3
30°	555.5	554.5	550.4	546.3	542.3	540.2	544.3	547.4	548.4	553.5	553.5
32.5°	520.9	513.8	506.7	502.6	500.6	499.5	500.6	504.6	504.6	510.7	517.8
35°	486.3	482.2	475.1	468.0	466.0	460.9	464.9	469.0	476.1	479.2	482.2
37.5°	448.7	443.6	440.5	438.5	434.4	435.4	432.4	438.5	444.6	443.6	445.6
40°	420.2	411.0	401.9	400.8	399.8	398.8	398.8	399.8	403.9	408.0	414.1
42.5°	383.6	380.5	372.4	364.2	362.2	360.2	358.1	362.2	370.3	377.4	380.5
45°	345.9	341.8	339.8	333.7	329.6	328.6	326.6	331.7	338.8	341.8	343.9
47.5°	311.3	310.3	304.2	305.2	302.2	303.2	302.2	305.2	305.2	308.3	310.3
50°	287.9	284.9	281.8	279.8	276.7	276.7	275.7	276.7	280.8	284.9	283.9
52.5°	264.5	259.4	258.4	257.4	255.4	257.4	254.3	255.4	259.4	261.5	260.5
55°	237.1	236.0	234.0	232.0	230.9	229.9	229.9	229.9	234.0	237.1	238.1
57.5°	215.7	210.6	206.5	206.5	202.5	201.4	203.5	204.5	207.5	209.6	211.6
60°	186.2	184.1	178.0	175.0	168.9	167.9	167.9	171.9	177.0	184.1	186.2
62.5°	154.6	151.6	150.6	150.6	150.6	150.6	150.6	150.6	150.6	151.6	151.6
65°	137.3	138.4	137.3	136.3	137.3	137.3	136.3	136.3	136.3	137.3	138.4
67.5°	123.1	122.1	123.1	122.1	121.1	121.1	120.1	121.1	122.1	123.1	123.1
70°	106.8	106.8	105.8	106.8	105.8	104.8	103.8	103.8	105.8	106.8	106.8
72.5°	91.6	91.6	90.5	90.5	88.5	88.5	89.5	88.5	88.5	91.6	91.6
75°	76.3	75.3	74.3	74.3	73.3	73.3	73.3	72.2	74.3	74.3	75.3
77.5°	60.0	60.0	60.0	59.0	59.0	58.0	58.0	59.0	59.0	59.0	60.0
80°	45.8	45.8	45.8	44.8	43.7	43.7	43.7	43.7	43.7	44.8	43.7
82.5°	31.5	31.5	31.5	31.5	31.5	30.5	30.5	30.5	31.5	31.5	30.5
85°	19.3	18.3	19.3	19.3	18.3	19.3	18.3	18.3	17.3	17.3	18.3
87.5°	8.1	7.1	6.1	6.1	7.1	6.1	6.1	6.1	7.1	6.1	6.1
90°	24.6	25.0	25.0	25.0	25.0	25.0	25.0	25.0	25.0	25.0	24.6
92.5°	53.8	50.7	49.9	46.9	47.7	46.2	47.7	46.9	49.9	50.7	53.8
95°	112.0	103.7	93.8	87.8	85.5	86.3	85.5	87.8	93.8	103.7	112.0
97.5°	224.8	202.1	172.5	157.4	149.1	144.5	149.1	157.4	172.5	202.1	224.8
100°	447.6	401.8	339.0	306.5	284.5	270.9	284.5	306.5	339.0	401.8	447.6
102.5°	756.8	707.6	638.0	576.7	547.9	528.2	547.9	576.7	638.0	707.6	756.8
105°	1002.3	989.8	942.9	896.0	863.5	852.9	863.5	896.0	942.9	989.8	1002.3
107.5°	1091.2	1106.4	1105.6	1098.8	1089.0	1071.6	1089.0	1098.8	1105.6	1106.4	1091.2
110°	1076.9	1107.9	1140.4	1154.8	1161.6	1160.9	1161.6	1154.8	1140.4	1107.9	1076.9

TEST NUMBER: P1010188

CATALOG NUMBER: S122RDIP-B675D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1028.1	1064.8	1113.2	1139.7	1154.1	1159.4	1154.1	1139.7	1113.2	1064.8	1028.1
115°	968.3	1007.3	1061.0	1095.8	1115.5	1122.3	1115.5	1095.8	1061.0	1007.3	968.3
117.5°	911.2	948.2	1003.5	1040.6	1061.0	1066.3	1061.0	1040.6	1003.5	948.2	911.2
120°	860.0	894.5	947.5	983.0	1005.0	1012.6	1005.0	983.0	947.5	894.5	860.0
122.5°	820.4	850.6	896.8	931.6	950.5	956.6	950.5	931.6	896.8	850.6	820.4
125°	784.4	812.8	856.7	885.4	904.3	910.4	904.3	885.4	856.7	812.8	784.4
127.5°	753.8	780.2	818.8	846.1	862.7	867.3	862.7	846.1	818.8	780.2	753.8
130°	722.7	747.7	784.8	810.5	825.6	831.7	825.6	810.5	784.8	747.7	722.7
132.5°	690.6	713.6	750.0	775.7	789.3	794.6	789.3	775.7	750.0	713.6	690.6
135°	659.2	680.3	712.9	737.8	751.5	754.5	751.5	737.8	712.9	680.3	659.2
137.5°	627.3	646.3	677.3	699.3	711.4	715.9	711.4	699.3	677.3	646.3	627.3
140°	599.4	616.0	640.2	659.9	671.3	675.8	671.3	659.9	640.2	616.0	599.4
142.5°	572.4	585.7	608.4	625.8	635.7	635.7	635.7	625.8	608.4	585.7	572.4
145°	550.6	561.5	579.7	592.5	600.1	602.4	600.1	592.5	579.7	561.5	550.6
147.5°	531.2	539.6	555.5	566.1	571.4	572.9	571.4	566.1	555.5	539.6	531.2
150°	514.6	521.4	532.8	541.8	546.4	547.1	546.4	541.8	532.8	521.4	514.6
152.5°	500.6	506.3	514.6	522.2	525.2	525.2	525.2	522.2	514.6	506.3	500.6
155°	487.0	491.1	499.5	504.8	507.8	506.3	507.8	504.8	499.5	491.1	487.0
157.5°	474.1	477.5	483.6	488.1	489.6	489.6	489.6	488.1	483.6	477.5	474.1
160°	461.2	463.9	469.2	473.0	473.7	473.7	473.7	473.0	469.2	463.9	461.2
162.5°	449.1	451.0	456.3	458.6	459.4	458.6	459.4	458.6	456.3	451.0	449.1
165°	437.4	438.9	442.0	445.0	445.0	444.2	445.0	445.0	442.0	438.9	437.4
167.5°	426.8	428.3	429.8	431.4	431.4	430.6	431.4	431.4	429.8	428.3	426.8
170°	417.0	417.7	418.5	420.8	420.0	418.5	420.0	420.8	418.5	417.7	417.0
172.5°	408.3	408.7	409.4	410.2	409.4	408.7	409.4	410.2	409.4	408.7	408.3
175°	401.5	401.8	401.8	402.6	401.8	400.3	401.8	402.6	401.8	401.8	401.5
177.5°	396.5	396.5	396.5	396.5	395.8	394.3	395.8	396.5	396.5	396.5	396.5
180°	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5

TEST NUMBER: P1010188

CATALOG NUMBER: S122RDIP-B675D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1394.8	1399.9	1397.9	1386.7	1397.9	1400.9	1407.0	1413.1	1417.2	1423.3	1428.4
5°	1307.3	1317.5	1323.6	1317.5	1337.9	1340.9	1355.2	1363.3	1375.5	1385.7	1393.8
7.5°	1224.9	1233.1	1245.3	1247.3	1259.5	1273.8	1294.1	1314.5	1333.8	1344.0	1353.1
10°	1136.4	1150.7	1169.0	1164.9	1183.2	1205.6	1227.0	1259.5	1275.8	1294.1	1310.4
12.5°	1047.9	1057.1	1081.5	1089.6	1116.1	1133.4	1162.9	1183.2	1223.9	1245.3	1259.5
15°	893.3	930.9	961.4	998.1	1032.6	1065.2	1091.7	1128.3	1163.9	1180.2	1203.6
17.5°	823.1	840.4	858.7	877.0	921.7	979.7	1026.5	1066.2	1096.7	1118.1	1145.6
20°	749.8	767.1	787.5	804.8	832.2	873.9	931.9	1000.1	1036.7	1059.1	1085.5
22.5°	697.9	714.2	727.4	742.7	764.1	794.6	838.3	922.8	971.6	999.1	1022.5
25°	642.0	662.3	676.6	687.8	705.0	738.6	774.2	822.0	909.5	930.9	963.5
27.5°	603.3	609.4	625.7	643.0	660.3	678.6	715.2	755.9	814.9	861.7	901.4
30°	557.5	572.8	588.0	595.2	610.4	636.9	659.3	703.0	748.8	785.4	833.2
32.5°	522.9	532.1	542.3	559.6	573.8	592.1	614.5	651.1	689.8	713.2	749.8
35°	484.3	490.4	511.7	518.9	533.1	551.4	573.8	602.3	644.0	662.3	688.8
37.5°	447.6	461.9	468.0	484.3	497.5	515.8	532.1	564.6	592.1	613.5	637.9
40°	419.2	425.3	436.5	450.7	461.9	476.1	496.5	519.9	549.4	566.7	588.0
42.5°	384.6	389.7	403.9	412.0	430.4	443.6	455.8	484.3	510.7	524.0	545.3
45°	346.9	359.1	368.3	384.6	394.7	411.0	426.3	446.6	471.0	486.3	498.5
47.5°	314.4	326.6	335.7	351.0	367.3	374.4	390.7	412.0	434.4	446.6	463.9
50°	287.9	292.0	309.3	316.4	333.7	347.9	359.1	377.4	401.9	409.0	423.2
52.5°	262.5	265.5	276.7	285.9	301.1	313.4	327.6	344.9	365.2	376.4	387.6
55°	240.1	242.1	247.2	257.4	267.6	282.8	296.1	312.3	329.6	341.8	352.0
57.5°	214.7	218.7	222.8	228.9	239.1	253.3	267.6	282.8	297.1	305.2	318.4
60°	185.2	191.3	198.4	205.5	212.6	222.8	239.1	253.3	266.6	273.7	283.9
62.5°	153.6	165.8	171.9	180.1	186.2	195.3	207.5	223.8	233.0	242.1	250.3
65°	138.4	139.4	140.4	148.5	159.7	168.9	180.1	192.3	206.5	212.6	218.7
67.5°	123.1	124.1	126.2	127.2	131.2	141.4	153.6	166.9	178.0	182.1	188.2
70°	107.8	107.8	111.9	112.9	113.9	115.0	125.1	138.4	148.5	153.6	160.7
72.5°	91.6	92.6	94.6	95.6	97.7	99.7	102.8	109.9	122.1	127.2	135.3
75°	75.3	76.3	77.3	78.3	81.4	82.4	85.5	89.5	94.6	100.7	105.8
77.5°	60.0	60.0	61.0	63.1	65.1	66.1	69.2	71.2	73.3	76.3	80.4
80°	44.8	45.8	45.8	47.8	47.8	48.8	49.9	52.9	54.9	57.0	59.0
82.5°	30.5	32.6	32.6	32.6	33.6	34.6	35.6	35.6	37.6	38.7	41.7
85°	18.3	19.3	19.3	19.3	18.3	20.3	20.3	21.4	21.4	21.4	22.4
87.5°	7.1	6.1	7.1	7.1	7.1	8.1	7.1	7.1	8.1	9.2	9.2
90°	24.2	22.7	24.2	25.0	25.7	25.0	20.4	15.1	11.4	10.2	9.1
92.5°	56.8	65.1	76.4	97.6	116.5	115.0	89.3	60.5	40.1	36.0	31.8
95°	120.3	152.1	198.3	259.6	296.7	262.6	174.8	109.0	74.2	65.1	56.0
97.5°	247.5	323.9	405.6	487.4	483.6	373.8	232.3	140.8	96.1	85.9	75.7
100°	493.4	597.1	690.9	706.8	597.8	411.7	248.2	155.9	115.8	105.2	94.6
102.5°	806.0	874.8	877.8	788.5	601.6	397.3	249.0	169.5	133.2	122.6	112.0
105°	1014.8	1005.0	919.5	762.1	560.8	377.6	252.8	185.4	149.8	139.2	128.7
107.5°	1076.1	1002.0	874.8	706.1	522.9	367.0	261.1	201.3	166.5	155.9	145.3
110°	1045.9	949.0	813.5	653.8	497.2	364.0	271.7	217.2	183.9	172.9	161.9

TEST NUMBER: P1010188

CATALOG NUMBER: S122RDIP-B675D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	991.4	886.2	757.5	617.5	480.5	364.8	283.0	232.3	200.5	189.2	177.8
115°	929.3	830.2	713.6	588.8	469.2	367.8	294.4	248.2	215.7	205.4	195.2
117.5°	874.1	781.7	677.3	569.1	463.1	372.3	306.5	262.6	232.3	221.7	211.1
120°	825.6	745.4	651.6	554.0	457.8	376.9	318.6	277.7	248.2	237.6	227.0
122.5°	790.1	715.1	631.1	541.1	454.8	382.2	329.2	292.1	264.9	253.9	242.9
125°	756.0	689.4	611.5	529.0	451.0	387.5	340.5	306.5	279.2	268.6	258.1
127.5°	727.3	663.7	591.8	517.6	448.8	392.8	351.1	320.1	293.6	282.6	271.7
130°	697.7	638.0	572.9	506.3	447.2	398.8	361.0	332.2	305.7	295.1	284.5
132.5°	667.5	613.7	554.7	497.2	446.5	404.9	370.8	342.8	317.8	307.2	296.7
135°	638.0	588.0	538.1	488.9	445.7	409.4	379.1	352.7	328.4	317.8	307.2
137.5°	608.4	567.6	524.4	482.8	445.7	414.0	386.0	361.0	336.8	327.0	317.1
140°	582.7	547.9	511.6	477.5	445.0	417.0	391.2	367.8	345.1	335.2	325.4
142.5°	559.2	530.5	501.0	472.2	445.0	419.2	395.8	373.1	351.1	342.0	333.0
145°	539.6	516.1	491.1	467.7	443.5	420.8	399.6	378.4	358.0	349.6	341.3
147.5°	522.9	504.0	483.6	463.1	441.2	421.5	401.8	382.9	363.2	355.6	348.1
150°	507.8	491.9	475.2	457.1	438.9	420.8	403.4	386.0	368.5	361.7	354.9
152.5°	494.9	482.1	466.9	451.8	435.1	419.2	404.1	389.0	373.8	367.8	361.7
155°	482.8	471.5	459.4	445.0	430.6	417.7	404.9	392.0	379.1	373.5	367.8
157.5°	470.7	460.9	450.3	438.9	426.1	414.7	404.9	394.3	382.9	378.0	373.1
160°	458.6	450.3	442.0	432.1	421.5	412.4	404.9	395.8	386.7	382.5	378.4
162.5°	447.2	440.4	433.6	426.1	417.7	410.2	404.1	396.5	389.0	386.0	382.9
165°	435.9	430.6	425.3	419.2	412.4	407.1	402.6	397.3	390.5	388.2	386.0
167.5°	425.3	421.5	417.0	412.4	407.9	404.1	401.8	397.3	392.0	390.5	389.0
170°	416.2	413.2	410.9	407.1	404.1	401.8	400.3	396.5	392.8	391.6	390.5
172.5°	407.9	405.6	404.1	401.8	399.6	398.8	398.1	395.8	393.5	392.8	392.0
175°	401.1	400.3	399.6	397.3	396.5	395.8	396.5	395.0	393.5	393.2	392.8
177.5°	396.5	395.8	395.8	394.3	393.5	394.3	395.8	394.3	393.5	393.5	393.5
180°	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5	393.5

TEST NUMBER: P1010188

CATALOG NUMBER: S122RDIP-B675D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1464.0	1464.0	1464.0	1464.0
2.5°	1437.6	1434.5	1452.8	1473.2
5°	1408.1	1413.1	1436.5	1465.0
7.5°	1377.5	1388.7	1416.2	1453.8
10°	1334.8	1355.2	1396.9	1435.5
12.5°	1293.1	1320.6	1360.2	1406.0
15°	1246.3	1276.8	1325.7	1380.6
17.5°	1194.4	1229.0	1286.0	1346.0
20°	1139.5	1185.3	1245.3	1310.4
22.5°	1078.4	1133.4	1195.4	1267.7
25°	1019.4	1079.4	1141.5	1224.9
27.5°	961.4	1020.4	1089.6	1174.1
30°	903.4	957.4	1031.6	1122.2
32.5°	841.4	897.3	975.7	1068.3
35°	784.4	840.4	913.6	1005.2
37.5°	723.4	783.4	853.6	948.2
40°	652.1	722.3	790.5	881.1
42.5°	593.1	667.4	733.5	819.0
45°	546.3	616.5	671.5	754.9
47.5°	502.6	559.6	615.5	692.8
50°	460.9	504.6	562.6	631.8
52.5°	418.1	455.8	505.6	570.8
55°	379.5	415.1	459.9	509.7
57.5°	343.9	369.3	414.1	458.8
60°	304.2	330.6	365.2	402.9
62.5°	270.6	291.0	323.5	355.1
65°	235.0	254.3	278.8	308.3
67.5°	202.5	219.8	239.1	262.5
70°	173.0	186.2	200.4	220.8
72.5°	141.4	155.7	168.9	185.2
75°	116.0	122.1	133.3	144.5
77.5°	89.5	97.7	103.8	112.9
80°	64.1	71.2	73.3	80.4
82.5°	42.7	46.8	50.9	52.9
85°	24.4	26.5	30.5	31.5
87.5°	9.2	10.2	12.2	14.2
90°	7.6	6.1	3.0	0.8
92.5°	25.7	21.9	15.9	11.4
95°	43.9	37.1	29.5	26.5
97.5°	62.1	52.2	43.9	39.4
100°	79.5	67.4	60.5	58.3
102.5°	96.1	84.0	77.2	75.7
105°	112.0	100.6	95.4	92.3
107.5°	128.7	118.1	112.8	110.5
110°	146.1	136.2	131.7	128.7

TEST NUMBER: P1010188

CATALOG NUMBER: S122RDIP-B675D725UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	162.7	153.6	148.3	145.3
115°	180.1	171.0	166.5	162.7
117.5°	196.8	188.4	183.9	180.9
120°	211.9	205.1	200.5	197.5
122.5°	227.8	220.2	215.7	213.4
125°	242.9	233.8	229.3	227.0
127.5°	257.3	247.5	241.4	238.4
130°	269.4	258.8	251.2	248.2
132.5°	280.8	269.4	261.1	257.3
135°	289.8	278.5	269.4	266.4
137.5°	299.7	287.6	278.5	274.7
140°	308.8	296.7	287.6	284.5
142.5°	317.1	305.0	296.7	294.4
145°	326.2	314.8	307.2	304.2
147.5°	335.2	324.7	317.1	314.8
150°	343.6	333.7	327.7	325.4
152.5°	351.1	342.8	336.8	336.0
155°	359.5	351.1	346.6	345.8
157.5°	366.3	358.7	354.9	354.2
160°	372.3	366.3	363.2	362.5
162.5°	377.6	373.1	370.1	370.8
165°	382.2	377.6	376.1	376.9
167.5°	386.0	382.9	381.4	382.2
170°	389.0	386.7	386.0	387.5
172.5°	391.2	389.0	389.7	390.5
175°	392.8	391.2	392.0	392.8
177.5°	393.5	392.0	392.8	394.3
180°	393.5	393.5	393.5	393.5

(END OF REPORT)