

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010205

Luminaire Tested: S122RDIP-B675D725UB40-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010205
REPORT IS A COMBINATION OF REPORTS P988567 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B675D725UB40-4F0-XX-W2A-A1
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5055.0 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010205

CATALOG NUMBER: S122RDIP-B675D725UB40-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1010205

CATALOG NUMBER: S122RDIP-B675D725UB40-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	99	95	91	88	91	88	84	82	74	72	70	62	61	59	51	50	49
2	90	84	78	73	83	77	73	68	66	62	59	56	53	51	46	44	43
3	83	74	67	62	77	69	63	58	59	55	51	50	47	44	41	39	37
4	76	66	59	53	71	62	55	50	53	48	44	45	41	38	38	35	33
5	71	60	52	46	65	56	49	44	48	43	39	41	37	34	34	32	29
6	65	54	46	41	60	50	43	39	44	38	34	37	33	30	32	29	26
7	61	49	41	36	56	46	39	34	40	35	31	34	30	27	29	26	24
8	56	45	37	32	52	42	35	31	37	31	28	32	28	25	27	24	22
9	53	41	34	29	49	39	32	28	34	29	25	29	25	22	25	22	20
10	49	38	31	26	46	36	29	25	31	26	23	27	23	21	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23247	23247	23247	23247
5°	23302	24693	23383	19726
10°	23046	26100	23209	16290
15°	22546	26107	22927	12237
20°	21943	21581	22421	10097
25°	21215	13485	21672	8588
30°	20283	8634	20834	7394
35°	19151	6635	19770	6327
40°	17887	5577	18652	5535
45°	16539	4747	17230	4647
50°	15156	4033	15864	4019
55°	13624	3505	14360	3460
60°	12265	2672	12915	2641
65°	10992	2012	11646	2282
70°	9593	1606	10342	1859
75°	8106	1231	8850	1407
80°	6435	837	6930	923
85°	4464	433	4902	456

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 21267 cd/sqm

TEST NUMBER: P1010205

CATALOG NUMBER: S122RDIP-B675D725UB40-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.3	2.8
10°-20°	388.8	7.7
20°-30°	500.4	9.9
30°-40°	474.7	9.4
40°-50°	406.9	8.0
50°-60°	309.9	6.1
60°-70°	195.4	3.9
70°-80°	97.5	1.9
80°-90°	27.6	0.5
90°-100°	55.6	1.1
100°-110°	176.9	3.5
110°-120°	302.6	6.0
120°-130°	398.0	7.9
130°-140°	446.8	8.8
140°-150°	438.1	8.7
150°-160°	367.5	7.3
160°-170°	243.7	4.8
170°-180°	85.2	1.7
0°-30°	1028.6	20.3
0°-40°	1503.3	29.7
0°-60°	2220.0	43.9
0°-90°	2540.6	50.3
90°-120°	535.2	10.6
90°-150°	1818.0	36.0
90°-180°	2514.0	49.7
0°-180°	5055.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1469	1469	1469	1469	1469	
5°	1470	1634	1475	1305	1470	139
15°	1385	1844	1408	864	1385	390
25°	1229	984	1255	627	1229	564
35°	1008	485	1041	462	1008	631
45°	757	337	789	330	757	585
55°	511	234	539	231	511	461
65°	309	122	328	138	309	307
75°	145	64	158	74	145	157
85°	32	18	35	19	32	36
90°	1	26	1	26	1	4
95°	40	47	40	47	40	44
105°	163	168	163	168	163	172
115°	304	304	304	304	304	300
125°	442	443	442	443	442	395
135°	572	578	572	578	572	442
145°	694	701	694	701	694	433
155°	793	799	793	799	793	365
165°	863	864	863	864	863	243
175°	898	895	898	895	898	85
180°	899	899	899	899	899	

TEST NUMBER: P1010205

CATALOG NUMBER: S122RDIP-B675D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6
2.5°	1477.8	1484.0	1487.0	1491.1	1500.3	1506.4	1515.6	1517.6	1516.6	1520.7	1509.5
5°	1469.7	1482.9	1495.2	1505.4	1521.7	1531.9	1543.1	1556.4	1559.5	1574.8	1565.6
7.5°	1458.4	1477.8	1495.2	1515.6	1540.1	1553.4	1570.7	1591.1	1600.3	1618.7	1623.8
10°	1440.1	1467.6	1497.2	1518.7	1552.3	1575.8	1592.1	1624.8	1646.2	1673.8	1669.7
12.5°	1410.5	1446.2	1486.0	1521.7	1565.6	1580.9	1611.5	1645.2	1672.8	1698.3	1720.7
15°	1385.0	1425.8	1469.7	1513.6	1563.6	1592.1	1622.8	1666.6	1696.2	1741.1	1760.5
17.5°	1350.3	1402.3	1454.4	1503.3	1562.5	1595.2	1633.0	1675.8	1719.7	1762.6	1777.9
20°	1314.5	1370.7	1426.8	1493.1	1560.5	1592.1	1630.9	1684.0	1726.9	1760.5	1760.5
22.5°	1271.7	1340.0	1404.3	1467.6	1541.1	1587.0	1626.8	1689.1	1719.7	1726.9	1699.3
25°	1228.8	1297.2	1367.6	1446.2	1529.9	1570.7	1615.6	1673.8	1684.0	1655.4	1584.0
27.5°	1177.8	1254.3	1333.9	1418.6	1506.4	1557.4	1598.3	1637.0	1617.7	1541.1	1429.9
30°	1125.7	1208.4	1298.2	1378.8	1485.0	1531.9	1566.6	1577.8	1516.6	1392.1	1248.2
32.5°	1071.6	1152.3	1247.2	1344.1	1451.3	1496.2	1518.7	1489.1	1376.8	1219.6	1044.1
35°	1008.4	1099.2	1198.2	1299.2	1405.4	1439.0	1452.3	1379.9	1235.9	1032.8	858.3
37.5°	951.2	1042.0	1148.2	1251.3	1354.3	1372.7	1359.4	1246.2	1063.5	862.4	692.0
40°	883.8	980.8	1084.9	1200.2	1284.9	1290.0	1257.4	1110.4	883.8	695.0	589.9
42.5°	821.6	919.6	1023.7	1141.0	1205.3	1188.0	1144.1	951.2	737.9	599.1	514.4
45°	757.3	850.2	962.4	1066.5	1112.5	1071.6	1005.3	800.2	619.5	515.4	450.1
47.5°	695.0	781.8	893.0	993.0	1001.2	955.3	876.7	670.5	536.8	453.1	400.1
50°	633.8	720.5	824.6	907.3	899.1	835.9	747.1	582.8	466.4	400.1	356.2
52.5°	572.6	651.1	752.2	817.5	782.8	721.6	633.8	494.0	407.2	349.0	315.4
55°	511.3	584.8	671.6	725.6	670.5	600.1	537.9	423.5	353.1	306.2	280.7
57.5°	460.3	518.5	598.1	630.7	564.4	509.3	455.2	364.4	306.2	272.5	242.9
60°	404.2	457.2	522.5	541.9	473.6	428.7	382.7	308.2	262.3	232.7	213.3
62.5°	356.2	400.1	450.1	450.1	389.9	356.2	321.5	258.2	220.4	197.0	187.8
65°	309.2	340.9	376.6	372.5	321.5	291.9	264.3	213.3	184.7	168.4	159.2
67.5°	263.3	287.8	311.3	297.0	260.3	234.7	209.2	172.5	153.1	141.9	129.6
70°	221.5	240.9	253.1	239.8	203.1	181.7	163.3	138.8	123.5	109.2	102.1
72.5°	185.7	193.9	198.0	181.7	151.0	138.8	125.5	108.2	94.9	87.8	85.7
75°	144.9	152.1	149.0	136.8	111.2	102.1	91.9	79.6	76.5	72.5	70.4
77.5°	113.3	113.3	108.2	97.0	79.6	72.5	68.4	62.3	59.2	58.2	56.1
80°	80.6	79.6	76.5	64.3	54.1	50.0	50.0	45.9	44.9	42.9	42.9
82.5°	53.1	53.1	49.0	38.8	35.7	34.7	33.7	31.6	31.6	30.6	30.6
85°	31.6	29.6	24.5	21.4	20.4	20.4	19.4	18.4	19.4	18.4	18.4
87.5°	14.3	11.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2
90°	0.8	2.8	4.8	6.9	8.9	9.9	11.8	15.5	19.2	22.9	26.6
92.5°	16.7	18.1	19.4	20.8	22.1	22.8	22.9	23.0	23.2	23.3	23.5
95°	39.5	41.2	42.9	44.6	46.3	47.1	47.3	47.6	47.9	48.3	48.6
97.5°	66.0	67.5	69.1	70.6	72.1	72.9	73.2	73.9	74.6	75.2	75.9
100°	96.4	97.8	99.1	100.5	101.8	102.5	102.7	103.2	103.7	104.2	104.7
102.5°	128.3	129.3	130.3	131.3	132.3	132.8	133.1	133.8	134.5	135.2	135.9
105°	163.2	163.7	164.2	164.7	165.2	165.5	165.7	166.0	166.3	166.7	167.0
107.5°	198.1	198.8	199.4	200.1	200.8	201.1	201.1	201.1	201.1	201.1	201.1
110°	231.5	232.5	233.5	234.5	235.5	236.0	236.0	236.0	236.0	236.0	236.0

TEST NUMBER: P1010205

CATALOG NUMBER: S122RDIP-B675D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	267.9	268.9	269.9	271.0	272.0	272.5	272.4	272.2	272.1	271.9	271.7
115°	303.6	304.6	305.6	306.6	307.6	308.1	307.9	307.6	307.3	306.9	306.6
117.5°	339.3	340.6	342.0	343.3	344.6	345.3	344.9	344.0	343.2	342.3	341.5
120°	374.9	376.3	377.6	379.0	380.3	381.0	380.3	379.0	377.6	376.3	374.9
122.5°	407.6	409.3	410.9	412.6	414.3	415.1	414.7	413.9	413.0	412.2	411.4
125°	441.7	443.2	444.7	446.2	447.7	448.5	448.3	447.8	447.3	446.8	446.3
127.5°	475.1	477.0	478.8	480.7	482.6	483.5	483.2	482.5	481.8	481.1	480.4
130°	506.2	508.4	510.6	512.8	515.0	516.1	515.9	515.6	515.3	514.9	514.6
132.5°	541.1	542.8	544.5	546.2	547.9	548.7	548.8	549.0	549.1	549.3	549.5
135°	571.5	573.3	575.2	577.0	578.9	579.8	580.0	580.3	580.7	581.0	581.4
137.5°	604.9	606.4	607.9	609.4	610.9	611.7	611.9	612.2	612.5	612.9	613.2
140°	634.5	636.0	637.5	639.0	640.5	641.3	641.7	642.6	643.4	644.3	645.1
142.5°	664.8	666.3	667.9	669.4	670.9	671.7	672.0	672.5	673.0	673.5	674.0
145°	693.7	694.9	696.1	697.2	698.4	699.0	699.5	700.5	701.6	702.6	703.6
147.5°	719.5	721.0	722.5	724.0	725.5	726.3	726.6	727.3	728.0	728.7	729.4
150°	746.1	747.1	748.1	749.1	750.1	750.6	750.9	751.6	752.3	752.9	753.6
152.5°	769.6	770.6	771.6	772.6	773.6	774.1	774.5	775.4	776.2	777.1	777.9
155°	793.1	793.6	794.1	794.6	795.1	795.4	795.7	796.2	796.7	797.2	797.7
157.5°	813.6	813.9	814.3	814.6	814.9	815.1	815.3	815.6	815.9	816.3	816.6
160°	831.8	832.1	832.5	832.8	833.1	833.3	833.4	833.6	833.7	833.9	834.1
162.5°	848.5	848.5	848.5	848.5	848.5	848.5	848.6	848.8	848.9	849.1	849.3
165°	862.9	862.7	862.6	862.4	862.3	862.2	862.2	862.2	862.2	862.2	862.2
167.5°	875.8	875.3	874.8	874.3	873.8	873.6	873.6	873.6	873.6	873.6	873.6
170°	885.7	885.2	884.7	884.2	883.7	883.4	883.3	883.2	883.0	882.9	882.7
172.5°	892.5	892.0	891.5	891.0	890.5	890.3	890.2	890.0	889.9	889.7	889.5
175°	897.8	897.3	896.8	896.3	895.8	895.6	895.4	895.1	894.7	894.4	894.0
177.5°	900.9	900.4	899.9	899.4	898.9	898.6	898.4	898.1	897.8	897.4	897.1
180°	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4

TEST NUMBER: P1010205

CATALOG NUMBER: S122RDIP-B675D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6
2.5°	1520.7	1522.7	1525.8	1540.1	1542.1	1546.2	1544.2	1544.2	1545.2	1543.1	1544.2
5°	1586.0	1589.1	1604.4	1621.7	1625.8	1621.7	1626.8	1634.0	1634.0	1634.0	1631.9
7.5°	1647.2	1658.5	1675.8	1701.3	1706.4	1711.5	1720.7	1714.6	1716.7	1725.8	1722.8
10°	1706.4	1722.8	1742.2	1763.6	1774.8	1782.0	1786.1	1795.2	1816.7	1792.2	1801.4
12.5°	1762.6	1786.1	1806.5	1829.9	1838.1	1847.3	1850.3	1858.5	1858.5	1857.5	1864.6
15°	1799.3	1820.8	1839.1	1854.4	1856.5	1854.4	1852.4	1853.4	1856.5	1844.2	1851.4
17.5°	1807.5	1809.5	1815.6	1809.5	1810.5	1789.1	1776.9	1773.8	1745.2	1746.2	1769.7
20°	1767.7	1733.0	1723.8	1690.1	1669.7	1614.6	1612.5	1597.2	1537.0	1555.4	1551.3
22.5°	1658.5	1599.3	1520.7	1481.9	1462.5	1404.3	1359.4	1327.8	1306.4	1284.9	1275.8
25°	1514.6	1418.6	1307.4	1230.8	1219.6	1165.5	1082.9	1044.1	998.1	983.9	1008.4
27.5°	1328.8	1204.3	1078.8	961.4	940.0	891.0	849.1	821.6	768.5	765.5	767.5
30°	1076.7	951.2	846.1	769.5	716.5	694.0	666.5	646.0	624.6	632.8	634.8
32.5°	884.9	765.5	667.5	626.6	602.2	587.9	564.4	551.1	541.9	538.9	537.9
35°	703.2	623.6	579.7	539.9	525.6	515.4	498.1	491.9	483.8	484.8	484.8
37.5°	602.2	535.8	503.2	482.7	469.5	464.4	453.1	447.0	441.9	439.9	442.9
40°	519.5	473.6	453.1	434.8	423.5	421.5	415.4	408.2	402.1	403.1	406.2
42.5°	459.3	432.7	408.2	394.0	385.8	382.7	377.6	372.5	372.5	369.5	368.4
45°	411.3	389.9	369.5	356.2	351.1	347.0	340.9	339.9	335.8	336.8	337.8
47.5°	368.4	351.1	335.8	322.5	317.4	316.4	310.3	306.2	306.2	305.2	304.1
50°	329.7	312.3	299.0	291.9	284.7	282.7	281.7	280.7	278.6	278.6	279.6
52.5°	298.0	280.7	270.5	264.3	260.3	258.2	258.2	257.2	257.2	257.2	256.2
55°	263.3	249.0	240.9	238.8	236.8	235.8	234.7	232.7	231.7	233.7	231.7
57.5°	230.7	225.6	218.4	216.4	211.3	211.3	208.2	206.2	204.1	206.2	206.2
60°	205.1	198.0	193.9	187.8	183.7	179.6	174.5	173.5	171.5	170.4	169.4
62.5°	178.6	172.5	162.3	153.1	147.0	142.9	140.8	139.8	139.8	138.8	138.8
65°	149.0	134.7	129.6	126.6	125.5	124.5	122.5	121.5	122.5	121.5	122.5
67.5°	116.3	114.3	111.2	109.2	108.2	107.2	107.2	106.1	106.1	106.1	106.1
70°	101.0	95.9	94.9	92.9	92.9	91.9	91.9	91.9	91.9	90.8	92.9
72.5°	83.7	80.6	79.6	78.6	78.6	78.6	77.6	77.6	77.6	76.5	77.6
75°	68.4	67.4	65.3	65.3	64.3	65.3	64.3	64.3	63.3	64.3	64.3
77.5°	55.1	54.1	53.1	53.1	52.1	52.1	52.1	52.1	52.1	52.1	53.1
80°	41.8	40.8	39.8	40.8	39.8	40.8	39.8	39.8	40.8	39.8	39.8
82.5°	30.6	29.6	29.6	28.6	28.6	28.6	28.6	28.6	28.6	28.6	28.6
85°	18.4	17.4	17.4	18.4	17.4	18.4	17.4	17.4	17.4	18.4	18.4
87.5°	8.2	9.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	9.2
90°	26.2	25.9	25.5	25.2	25.0	25.1	25.3	25.4	25.6	25.8	25.6
92.5°	23.7	23.9	24.0	24.2	24.3	24.3	24.3	24.3	24.3	24.3	24.3
95°	48.6	48.6	48.6	48.6	48.6	48.4	48.1	47.8	47.4	47.1	47.4
97.5°	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9
100°	104.7	104.7	104.7	104.7	104.7	104.6	104.5	104.3	104.2	104.0	104.2
102.5°	136.1	136.2	136.4	136.5	136.6	136.5	136.4	136.2	136.1	135.9	136.1
105°	167.3	167.7	168.0	168.3	168.5	168.5	168.5	168.5	168.5	168.5	168.5
107.5°	201.3	201.5	201.6	201.8	201.9	201.5	200.6	199.8	198.9	198.1	198.9
110°	236.0	236.0	236.0	236.0	236.0	235.8	235.3	234.8	234.3	233.8	234.3

TEST NUMBER: P1010205

CATALOG NUMBER: S122RDIP-B675D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	271.2	270.7	270.2	269.7	269.4	269.2	268.9	268.6	268.2	267.9	268.2
115°	306.4	306.3	306.1	306.0	305.9	305.6	305.1	304.6	304.1	303.6	304.1
117.5°	341.0	340.5	340.0	339.5	339.3	339.0	338.5	338.0	337.5	337.0	337.5
120°	374.9	374.9	374.9	374.9	374.9	374.6	374.1	373.6	373.1	372.6	373.1
122.5°	410.9	410.4	409.9	409.4	409.1	408.9	408.6	408.3	407.9	407.6	407.9
125°	445.8	445.3	444.8	444.3	444.0	443.9	443.7	443.6	443.4	443.2	443.4
127.5°	479.7	479.1	478.4	477.7	477.4	477.1	476.6	476.1	475.6	475.1	475.6
130°	514.3	513.9	513.6	513.3	513.1	512.8	512.1	511.4	510.7	510.0	510.7
132.5°	548.7	547.8	547.0	546.1	545.7	545.4	544.9	544.4	543.9	543.4	543.9
135°	581.2	581.0	580.9	580.7	580.6	580.3	579.8	579.3	578.8	578.3	578.8
137.5°	613.0	612.9	612.7	612.6	612.5	612.2	611.5	610.8	610.1	609.4	610.1
140°	645.1	645.1	645.1	645.1	645.1	644.8	644.1	643.4	642.8	642.1	642.8
142.5°	674.2	674.3	674.5	674.6	674.7	674.4	673.7	673.0	672.4	671.7	672.4
145°	703.8	703.9	704.1	704.2	704.3	704.0	703.3	702.6	702.0	701.3	702.0
147.5°	729.7	730.1	730.4	730.7	730.9	730.6	729.9	729.2	728.5	727.8	728.5
150°	754.1	754.6	755.1	755.6	755.9	755.6	755.1	754.6	754.1	753.6	754.1
152.5°	778.6	779.3	780.0	780.7	781.0	780.7	780.0	779.3	778.6	777.9	778.6
155°	798.5	799.4	800.2	801.1	801.5	801.2	800.7	800.2	799.7	799.2	799.7
157.5°	817.8	819.0	820.1	821.3	821.9	821.5	820.7	819.8	819.0	818.2	819.0
160°	835.1	836.1	837.1	838.1	838.6	838.3	837.6	836.9	836.3	835.6	836.3
162.5°	850.5	851.7	852.8	854.0	854.6	854.2	853.3	852.5	851.6	850.8	851.6
165°	863.4	864.6	865.7	866.9	867.5	867.1	866.2	865.4	864.5	863.7	864.5
167.5°	874.8	876.0	877.1	878.3	878.9	878.5	877.6	876.8	875.9	875.1	875.9
170°	883.9	885.1	886.2	887.4	888.0	887.5	886.5	885.4	884.4	883.4	884.4
172.5°	890.7	891.9	893.0	894.2	894.8	894.3	893.3	892.3	891.3	890.3	891.3
175°	895.2	896.4	897.6	898.8	899.4	898.9	897.9	896.8	895.8	894.8	895.8
177.5°	898.1	899.1	900.1	901.1	901.6	901.1	900.1	899.1	898.1	897.1	898.1
180°	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4

TEST NUMBER: P1010205

CATALOG NUMBER: S122RDIP-B675D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6
2.5°	1548.3	1541.1	1539.1	1541.1	1539.1	1540.1	1532.9	1506.4	1513.6	1502.3	1508.4
5°	1636.0	1629.9	1616.6	1614.6	1612.5	1610.5	1600.3	1576.8	1567.6	1552.3	1551.3
7.5°	1719.7	1719.7	1709.5	1702.4	1693.2	1686.0	1672.8	1638.1	1623.8	1605.4	1595.2
10°	1802.4	1775.8	1787.1	1779.9	1757.5	1753.4	1728.9	1708.5	1680.9	1662.6	1646.2
12.5°	1861.6	1853.4	1843.2	1837.1	1831.0	1817.7	1801.4	1749.3	1735.0	1698.3	1679.9
15°	1859.5	1854.4	1857.5	1857.5	1855.5	1852.4	1839.1	1801.4	1776.9	1741.1	1709.5
17.5°	1759.5	1772.8	1786.1	1795.2	1815.6	1824.8	1837.1	1814.6	1799.3	1768.7	1735.0
20°	1585.0	1617.7	1656.4	1664.6	1683.0	1737.1	1761.6	1780.9	1787.1	1776.9	1749.3
22.5°	1342.1	1369.6	1463.5	1461.5	1488.0	1552.3	1623.8	1682.0	1727.9	1753.4	1743.2
25°	1051.2	1090.0	1140.0	1177.8	1264.5	1360.5	1449.3	1542.1	1621.7	1692.2	1709.5
27.5°	795.0	846.1	885.9	935.9	979.8	1093.1	1207.4	1352.3	1445.2	1578.9	1648.3
30°	643.0	666.5	706.3	729.7	751.2	837.9	967.5	1110.4	1273.7	1427.8	1547.2
32.5°	549.1	565.4	595.0	605.2	627.7	685.8	767.5	898.1	1066.5	1253.3	1410.5
35°	493.0	510.3	516.4	525.6	544.0	580.7	636.9	731.8	883.8	1066.5	1254.3
37.5°	445.0	454.2	471.5	477.6	483.8	511.3	549.1	615.4	716.5	866.5	1074.7
40°	411.3	416.4	425.6	430.7	434.8	454.2	487.8	532.8	607.3	721.6	913.4
42.5°	375.6	381.7	387.8	394.0	399.1	414.4	434.8	477.6	527.7	614.4	753.2
45°	340.9	345.0	352.1	356.2	363.3	375.6	394.0	423.5	468.5	523.6	635.8
47.5°	309.2	314.3	317.4	322.5	327.6	340.9	358.2	377.6	414.4	468.5	550.1
50°	280.7	286.8	290.9	291.9	296.0	308.2	322.5	343.9	367.4	409.3	480.7
52.5°	260.3	261.3	264.3	268.4	267.4	274.5	287.8	304.1	328.6	362.3	414.4
55°	236.8	239.8	241.9	242.9	242.9	249.0	256.2	271.5	290.9	318.4	362.3
57.5°	207.2	210.2	216.4	218.4	221.5	224.5	227.6	237.8	254.1	280.7	316.4
60°	176.6	178.6	184.7	188.8	190.9	199.0	203.1	211.3	220.4	239.8	273.5
62.5°	141.9	143.9	147.0	151.0	155.1	167.4	177.6	185.7	192.9	206.2	233.7
65°	123.5	124.5	126.6	127.6	128.6	133.7	142.9	154.1	167.4	177.6	193.9
67.5°	107.2	108.2	109.2	111.2	112.3	113.3	117.4	120.4	133.7	148.0	160.2
70°	91.9	93.9	94.9	94.9	95.9	98.0	100.0	104.1	108.2	115.3	130.6
72.5°	77.6	78.6	80.6	80.6	80.6	82.7	84.7	86.8	88.8	92.9	99.0
75°	64.3	66.3	66.3	66.3	67.4	67.4	69.4	71.4	73.5	76.5	78.6
77.5°	53.1	53.1	53.1	53.1	54.1	54.1	55.1	57.2	58.2	59.2	61.2
80°	39.8	40.8	40.8	40.8	41.8	41.8	41.8	43.9	44.9	44.9	46.9
82.5°	29.6	29.6	29.6	30.6	29.6	30.6	30.6	31.6	30.6	31.6	32.7
85°	18.4	18.4	18.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4	20.4
87.5°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	10.2	9.2	9.2
90°	25.4	25.3	25.1	25.0	25.2	25.5	25.9	26.2	26.6	22.9	19.2
92.5°	24.3	24.3	24.3	24.3	24.2	24.0	23.9	23.7	23.5	23.3	23.2
95°	47.8	48.1	48.4	48.6	48.6	48.6	48.6	48.6	48.6	48.3	47.9
97.5°	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.2	74.6
100°	104.3	104.5	104.6	104.7	104.7	104.7	104.7	104.7	104.7	104.2	103.7
102.5°	136.2	136.4	136.5	136.6	136.5	136.4	136.2	136.1	135.9	135.2	134.5
105°	168.5	168.5	168.5	168.5	168.3	168.0	167.7	167.3	167.0	166.7	166.3
107.5°	199.8	200.6	201.5	201.9	201.8	201.6	201.5	201.3	201.1	201.1	201.1
110°	234.8	235.3	235.8	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0

TEST NUMBER: P1010205

CATALOG NUMBER: S122RDIP-B675D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	268.6	268.9	269.2	269.4	269.7	270.2	270.7	271.2	271.7	271.9	272.1
115°	304.6	305.1	305.6	305.9	306.0	306.1	306.3	306.4	306.6	306.9	307.3
117.5°	338.0	338.5	339.0	339.3	339.5	340.0	340.5	341.0	341.5	342.3	343.2
120°	373.6	374.1	374.6	374.9	374.9	374.9	374.9	374.9	374.9	376.3	377.6
122.5°	408.3	408.6	408.9	409.1	409.4	409.9	410.4	410.9	411.4	412.2	413.0
125°	443.6	443.7	443.9	444.0	444.3	444.8	445.3	445.8	446.3	446.8	447.3
127.5°	476.1	476.6	477.1	477.4	477.7	478.4	479.1	479.7	480.4	481.1	481.8
130°	511.4	512.1	512.8	513.1	513.3	513.6	513.9	514.3	514.6	514.9	515.3
132.5°	544.4	544.9	545.4	545.7	546.1	547.0	547.8	548.7	549.5	549.3	549.1
135°	579.3	579.8	580.3	580.6	580.7	580.9	581.0	581.2	581.4	581.0	580.7
137.5°	610.8	611.5	612.2	612.5	612.6	612.7	612.9	613.0	613.2	612.9	612.5
140°	643.4	644.1	644.8	645.1	645.1	645.1	645.1	645.1	645.1	644.3	643.4
142.5°	673.0	673.7	674.4	674.7	674.6	674.5	674.3	674.2	674.0	673.5	673.0
145°	702.6	703.3	704.0	704.3	704.2	704.1	703.9	703.8	703.6	702.6	701.6
147.5°	729.2	729.9	730.6	730.9	730.7	730.4	730.1	729.7	729.4	728.7	728.0
150°	754.6	755.1	755.6	755.9	755.6	755.1	754.6	754.1	753.6	752.9	752.3
152.5°	779.3	780.0	780.7	781.0	780.7	780.0	779.3	778.6	777.9	777.1	776.2
155°	800.2	800.7	801.2	801.5	801.1	800.2	799.4	798.5	797.7	797.2	796.7
157.5°	819.8	820.7	821.5	821.9	821.3	820.1	819.0	817.8	816.6	816.3	815.9
160°	836.9	837.6	838.3	838.6	838.1	837.1	836.1	835.1	834.1	833.9	833.7
162.5°	852.5	853.3	854.2	854.6	854.0	852.8	851.7	850.5	849.3	849.1	848.9
165°	865.4	866.2	867.1	867.5	866.9	865.7	864.6	863.4	862.2	862.2	862.2
167.5°	876.8	877.6	878.5	878.9	878.3	877.1	876.0	874.8	873.6	873.6	873.6
170°	885.4	886.5	887.5	888.0	887.4	886.2	885.1	883.9	882.7	882.9	883.0
172.5°	892.3	893.3	894.3	894.8	894.2	893.0	891.9	890.7	889.5	889.7	889.9
175°	896.8	897.9	898.9	899.4	898.8	897.6	896.4	895.2	894.0	894.4	894.7
177.5°	899.1	900.1	901.1	901.6	901.1	900.1	899.1	898.1	897.1	897.4	897.8
180°	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4

TEST NUMBER: P1010205

CATALOG NUMBER: S122RDIP-B675D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6
2.5°	1499.3	1494.2	1494.2	1491.1	1491.1	1474.8	1474.8	1479.9	1473.7	1466.6	1456.4
5°	1538.0	1526.8	1523.8	1519.7	1506.4	1486.0	1477.8	1474.8	1462.5	1447.2	1429.9
7.5°	1574.8	1556.4	1547.2	1538.0	1520.7	1492.1	1475.8	1464.6	1446.2	1422.7	1400.3
10°	1610.5	1587.0	1563.6	1552.3	1527.8	1492.1	1468.6	1450.3	1423.7	1392.1	1360.5
12.5°	1643.2	1594.2	1590.1	1567.6	1531.9	1491.1	1455.4	1428.8	1395.2	1358.4	1321.7
15°	1671.7	1621.7	1597.2	1576.8	1529.9	1478.9	1441.1	1408.4	1363.5	1321.7	1276.8
17.5°	1686.0	1631.9	1615.6	1581.9	1534.0	1467.6	1416.6	1376.8	1327.8	1277.8	1226.8
20°	1700.3	1637.0	1610.5	1587.0	1521.7	1446.2	1389.0	1343.1	1289.0	1229.8	1173.7
22.5°	1707.5	1637.0	1605.4	1572.7	1509.5	1422.7	1355.4	1301.3	1238.0	1177.8	1110.4
25°	1695.2	1630.9	1593.2	1559.5	1488.0	1394.1	1316.6	1255.3	1188.0	1119.6	1051.2
27.5°	1664.6	1616.6	1572.7	1538.0	1458.4	1357.4	1275.8	1206.4	1136.9	1060.4	991.0
30°	1607.4	1586.0	1551.3	1512.5	1425.8	1324.7	1227.8	1156.3	1079.8	1003.3	930.8
32.5°	1518.7	1537.0	1514.6	1480.9	1387.0	1279.8	1176.8	1104.3	1020.6	937.9	871.6
35°	1410.5	1475.8	1463.5	1440.1	1346.2	1231.9	1128.8	1041.0	957.3	873.6	807.3
37.5°	1292.1	1391.1	1401.3	1387.0	1299.2	1182.9	1069.6	983.9	898.1	813.4	746.1
40°	1129.8	1281.9	1314.5	1320.7	1250.2	1123.7	1005.3	921.6	836.9	754.2	672.6
42.5°	980.8	1172.7	1213.5	1239.0	1188.0	1065.5	946.1	853.2	769.5	695.0	613.4
45°	841.0	1041.0	1107.4	1140.0	1117.6	999.2	875.7	788.9	712.4	644.0	565.4
47.5°	697.1	898.1	991.0	1043.1	1043.1	931.8	808.3	722.6	649.1	590.9	521.5
50°	601.1	768.5	864.4	932.8	951.2	863.4	747.1	663.4	594.0	530.7	477.6
52.5°	512.3	662.4	742.0	813.4	866.5	789.9	678.7	603.2	534.8	475.6	433.8
55°	442.9	555.2	627.7	706.3	765.5	715.4	612.4	538.9	479.7	430.7	395.0
57.5°	376.6	474.6	533.8	603.2	666.5	628.7	546.0	482.7	430.7	387.8	356.2
60°	320.5	400.1	446.0	500.1	578.7	552.1	483.8	425.6	383.7	345.0	318.4
62.5°	272.5	335.8	374.6	413.3	484.8	472.5	419.5	374.6	338.8	306.2	283.7
65°	223.5	275.6	306.2	339.9	397.0	402.1	359.3	327.6	295.0	266.4	246.0
67.5°	180.6	221.5	249.0	277.6	323.5	337.8	308.2	281.7	254.1	230.7	212.3
70°	145.9	174.5	194.9	217.4	255.2	272.5	257.2	238.8	216.4	197.0	180.6
72.5°	115.3	133.7	145.9	163.3	193.9	211.3	210.2	193.9	177.6	164.3	151.0
75°	84.7	99.0	109.2	120.4	144.9	161.3	165.3	158.2	141.9	131.7	121.5
77.5°	64.3	72.5	77.6	85.7	103.1	117.4	123.5	121.5	110.2	102.1	94.9
80°	49.0	51.0	53.1	56.1	70.4	83.7	87.8	86.8	80.6	77.6	69.4
82.5°	34.7	35.7	36.7	37.8	42.9	54.1	58.2	60.2	55.1	52.1	44.9
85°	20.4	21.4	21.4	23.5	24.5	27.6	34.7	34.7	33.7	29.6	28.6
87.5°	10.2	10.2	9.2	9.2	10.2	11.2	13.3	15.3	13.3	12.2	11.2
90°	15.5	11.8	9.9	8.9	6.9	4.8	2.8	0.8	2.8	4.8	6.9
92.5°	23.0	22.9	22.8	22.1	20.8	19.4	18.1	16.7	18.1	19.4	20.8
95°	47.6	47.3	47.1	46.3	44.6	42.9	41.2	39.5	41.2	42.9	44.6
97.5°	73.9	73.2	72.9	72.1	70.6	69.1	67.5	66.0	67.5	69.1	70.6
100°	103.2	102.7	102.5	101.8	100.5	99.1	97.8	96.4	97.8	99.1	100.5
102.5°	133.8	133.1	132.8	132.3	131.3	130.3	129.3	128.3	129.3	130.3	131.3
105°	166.0	165.7	165.5	165.2	164.7	164.2	163.7	163.2	163.7	164.2	164.7
107.5°	201.1	201.1	201.1	200.8	200.1	199.4	198.8	198.1	198.8	199.4	200.1
110°	236.0	236.0	236.0	235.5	234.5	233.5	232.5	231.5	232.5	233.5	234.5

TEST NUMBER: P1010205

CATALOG NUMBER: S122RDIP-B675D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	272.2	272.4	272.5	272.0	271.0	269.9	268.9	267.9	268.9	269.9	271.0
115°	307.6	307.9	308.1	307.6	306.6	305.6	304.6	303.6	304.6	305.6	306.6
117.5°	344.0	344.9	345.3	344.6	343.3	342.0	340.6	339.3	340.6	342.0	343.3
120°	379.0	380.3	381.0	380.3	379.0	377.6	376.3	374.9	376.3	377.6	379.0
122.5°	413.9	414.7	415.1	414.3	412.6	410.9	409.3	407.6	409.3	410.9	412.6
125°	447.8	448.3	448.5	447.7	446.2	444.7	443.2	441.7	443.2	444.7	446.2
127.5°	482.5	483.2	483.5	482.6	480.7	478.8	477.0	475.1	477.0	478.8	480.7
130°	515.6	515.9	516.1	515.0	512.8	510.6	508.4	506.2	508.4	510.6	512.8
132.5°	549.0	548.8	548.7	547.9	546.2	544.5	542.8	541.1	542.8	544.5	546.2
135°	580.3	580.0	579.8	578.9	577.0	575.2	573.3	571.5	573.3	575.2	577.0
137.5°	612.2	611.9	611.7	610.9	609.4	607.9	606.4	604.9	606.4	607.9	609.4
140°	642.6	641.7	641.3	640.5	639.0	637.5	636.0	634.5	636.0	637.5	639.0
142.5°	672.5	672.0	671.7	670.9	669.4	667.9	666.3	664.8	666.3	667.9	669.4
145°	700.5	699.5	699.0	698.4	697.2	696.1	694.9	693.7	694.9	696.1	697.2
147.5°	727.3	726.6	726.3	725.5	724.0	722.5	721.0	719.5	721.0	722.5	724.0
150°	751.6	750.9	750.6	750.1	749.1	748.1	747.1	746.1	747.1	748.1	749.1
152.5°	775.4	774.5	774.1	773.6	772.6	771.6	770.6	769.6	770.6	771.6	772.6
155°	796.2	795.7	795.4	795.1	794.6	794.1	793.6	793.1	793.6	794.1	794.6
157.5°	815.6	815.3	815.1	814.9	814.6	814.3	813.9	813.6	813.9	814.3	814.6
160°	833.6	833.4	833.3	833.1	832.8	832.5	832.1	831.8	832.1	832.5	832.8
162.5°	848.8	848.6	848.5	848.5	848.5	848.5	848.5	848.5	848.5	848.5	848.5
165°	862.2	862.2	862.2	862.3	862.4	862.6	862.7	862.9	862.7	862.6	862.4
167.5°	873.6	873.6	873.6	873.8	874.3	874.8	875.3	875.8	875.3	874.8	874.3
170°	883.2	883.3	883.4	883.7	884.2	884.7	885.2	885.7	885.2	884.7	884.2
172.5°	890.0	890.2	890.3	890.5	891.0	891.5	892.0	892.5	892.0	891.5	891.0
175°	895.1	895.4	895.6	895.8	896.3	896.8	897.3	897.8	897.3	896.8	896.3
177.5°	898.1	898.4	898.6	898.9	899.4	899.9	900.4	900.9	900.4	899.9	899.4
180°	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4

TEST NUMBER: P1010205

CATALOG NUMBER: S122RDIP-B675D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6
2.5°	1452.3	1453.3	1456.4	1447.2	1432.9	1426.8	1408.4	1405.4	1402.3	1402.3	1405.4
5°	1419.7	1415.6	1416.6	1399.2	1378.8	1366.6	1341.1	1345.2	1331.9	1323.7	1325.8
7.5°	1383.9	1372.7	1371.7	1349.2	1323.7	1301.3	1274.7	1268.6	1256.4	1242.1	1235.9
10°	1339.0	1330.9	1315.6	1290.0	1257.4	1239.0	1203.3	1181.9	1178.8	1157.4	1149.2
12.5°	1293.1	1278.8	1263.5	1227.8	1191.0	1161.4	1134.9	1111.4	1095.1	1076.7	1064.5
15°	1240.0	1222.7	1205.3	1167.6	1124.7	1095.1	1055.3	1020.6	972.6	934.9	913.4
17.5°	1181.9	1162.5	1139.0	1097.1	1055.3	1014.5	941.0	900.2	866.5	844.0	830.8
20°	1121.6	1100.2	1076.7	1034.9	962.4	891.0	850.2	818.5	798.1	775.7	759.3
22.5°	1058.4	1035.9	1010.4	945.1	868.5	818.5	786.9	757.3	727.7	715.4	707.3
25°	999.2	978.8	946.1	857.3	797.1	751.2	715.4	696.0	680.7	664.4	649.1
27.5°	937.9	900.2	854.2	779.7	742.0	695.0	669.5	655.2	628.7	617.5	610.3
30°	864.4	822.6	778.7	725.6	681.8	649.1	625.6	602.2	586.8	575.6	563.4
32.5°	789.9	750.1	722.6	667.5	634.8	601.1	578.7	564.4	541.9	534.8	529.7
35°	725.6	692.0	667.5	622.6	591.9	561.3	545.0	523.6	509.3	496.0	487.8
37.5°	662.4	644.0	618.5	580.7	548.1	523.6	501.1	494.0	474.6	467.4	459.3
40°	618.5	590.9	569.5	536.8	509.3	482.7	468.5	452.1	438.9	427.6	424.6
42.5°	565.4	545.0	532.8	497.0	468.5	453.1	435.8	417.4	407.2	398.0	386.8
45°	525.6	507.2	489.9	461.3	435.8	416.4	401.1	388.8	371.5	367.4	350.1
47.5°	483.8	465.4	452.1	423.5	400.1	381.7	370.5	354.1	339.9	330.7	322.5
50°	441.9	426.6	414.4	389.9	369.5	350.1	334.8	318.4	312.3	297.0	291.9
52.5°	402.1	391.9	378.6	355.2	334.8	318.4	302.1	288.8	279.6	271.5	265.4
55°	368.4	352.1	346.0	320.5	303.1	285.8	271.5	263.3	252.1	247.0	241.9
57.5°	330.7	321.5	311.3	291.9	272.5	256.2	246.0	233.7	227.6	221.5	217.4
60°	298.0	284.7	276.6	260.3	242.9	227.6	218.4	209.2	201.1	196.0	187.8
62.5°	260.3	250.0	244.9	227.6	213.3	199.0	190.9	181.7	175.5	166.4	156.2
65°	227.6	219.4	213.3	199.0	185.7	172.5	164.3	153.1	144.9	139.8	138.8
67.5°	199.0	192.9	183.7	170.4	157.2	147.0	137.8	128.6	127.6	125.5	125.5
70°	167.4	161.3	156.2	141.9	130.6	119.4	117.4	114.3	111.2	110.2	108.2
72.5°	139.8	134.7	128.6	116.3	105.1	102.1	100.0	98.0	94.9	93.9	92.9
75°	113.3	106.1	102.1	90.8	87.8	85.7	83.7	80.6	78.6	77.6	75.5
77.5°	86.8	79.6	79.6	73.5	71.4	68.4	66.3	64.3	63.3	61.2	61.2
80°	61.2	61.2	59.2	56.1	53.1	52.1	49.0	48.0	46.9	48.0	45.9
82.5°	44.9	40.8	40.8	38.8	36.7	35.7	33.7	33.7	32.7	32.7	32.7
85°	25.5	25.5	24.5	22.5	21.4	21.4	20.4	20.4	19.4	19.4	18.4
87.5°	10.2	9.2	10.2	9.2	9.2	8.2	8.2	8.2	7.1	8.2	7.1
90°	8.9	9.9	11.8	15.5	19.2	22.9	26.6	26.2	25.9	25.5	25.2
92.5°	22.1	22.8	22.9	23.0	23.2	23.3	23.5	23.7	23.9	24.0	24.2
95°	46.3	47.1	47.3	47.6	47.9	48.3	48.6	48.6	48.6	48.6	48.6
97.5°	72.1	72.9	73.2	73.9	74.6	75.2	75.9	75.9	75.9	75.9	75.9
100°	101.8	102.5	102.7	103.2	103.7	104.2	104.7	104.7	104.7	104.7	104.7
102.5°	132.3	132.8	133.1	133.8	134.5	135.2	135.9	136.1	136.2	136.4	136.5
105°	165.2	165.5	165.7	166.0	166.3	166.7	167.0	167.3	167.7	168.0	168.3
107.5°	200.8	201.1	201.1	201.1	201.1	201.1	201.1	201.3	201.5	201.6	201.8
110°	235.5	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0

TEST NUMBER: P1010205

CATALOG NUMBER: S122RDIP-B675D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	272.0	272.5	272.4	272.2	272.1	271.9	271.7	271.2	270.7	270.2	269.7
115°	307.6	308.1	307.9	307.6	307.3	306.9	306.6	306.4	306.3	306.1	306.0
117.5°	344.6	345.3	344.9	344.0	343.2	342.3	341.5	341.0	340.5	340.0	339.5
120°	380.3	381.0	380.3	379.0	377.6	376.3	374.9	374.9	374.9	374.9	374.9
122.5°	414.3	415.1	414.7	413.9	413.0	412.2	411.4	410.9	410.4	409.9	409.4
125°	447.7	448.5	448.3	447.8	447.3	446.8	446.3	445.8	445.3	444.8	444.3
127.5°	482.6	483.5	483.2	482.5	481.8	481.1	480.4	479.7	479.1	478.4	477.7
130°	515.0	516.1	515.9	515.6	515.3	514.9	514.6	514.3	513.9	513.6	513.3
132.5°	547.9	548.7	548.8	549.0	549.1	549.3	549.5	548.7	547.8	547.0	546.1
135°	578.9	579.8	580.0	580.3	580.7	581.0	581.4	581.2	581.0	580.9	580.7
137.5°	610.9	611.7	611.9	612.2	612.5	612.9	613.2	613.0	612.9	612.7	612.6
140°	640.5	641.3	641.7	642.6	643.4	644.3	645.1	645.1	645.1	645.1	645.1
142.5°	670.9	671.7	672.0	672.5	673.0	673.5	674.0	674.2	674.3	674.5	674.6
145°	698.4	699.0	699.5	700.5	701.6	702.6	703.6	703.8	703.9	704.1	704.2
147.5°	725.5	726.3	726.6	727.3	728.0	728.7	729.4	729.7	730.1	730.4	730.7
150°	750.1	750.6	750.9	751.6	752.3	752.9	753.6	754.1	754.6	755.1	755.6
152.5°	773.6	774.1	774.5	775.4	776.2	777.1	777.9	778.6	779.3	780.0	780.7
155°	795.1	795.4	795.7	796.2	796.7	797.2	797.7	798.5	799.4	800.2	801.1
157.5°	814.9	815.1	815.3	815.6	815.9	816.3	816.6	817.8	819.0	820.1	821.3
160°	833.1	833.3	833.4	833.6	833.7	833.9	834.1	835.1	836.1	837.1	838.1
162.5°	848.5	848.5	848.6	848.8	848.9	849.1	849.3	850.5	851.7	852.8	854.0
165°	862.3	862.2	862.2	862.2	862.2	862.2	862.2	863.4	864.6	865.7	866.9
167.5°	873.8	873.6	873.6	873.6	873.6	873.6	873.6	874.8	876.0	877.1	878.3
170°	883.7	883.4	883.3	883.2	883.0	882.9	882.7	883.9	885.1	886.2	887.4
172.5°	890.5	890.3	890.2	890.0	889.9	889.7	889.5	890.7	891.9	893.0	894.2
175°	895.8	895.6	895.4	895.1	894.7	894.4	894.0	895.2	896.4	897.6	898.8
177.5°	898.9	898.6	898.4	898.1	897.8	897.4	897.1	898.1	899.1	900.1	901.1
180°	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4

TEST NUMBER: P1010205

CATALOG NUMBER: S122RDIP-B675D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6
2.5°	1405.4	1403.3	1397.2	1399.2	1396.2	1396.2	1394.1	1394.1	1394.1	1399.2	1396.2
5°	1328.8	1321.7	1314.5	1311.5	1308.4	1305.3	1305.3	1304.3	1313.5	1311.5	1319.6
7.5°	1233.9	1231.9	1217.6	1217.6	1212.5	1210.4	1215.5	1216.6	1217.6	1219.6	1224.7
10°	1149.2	1144.1	1123.7	1125.7	1122.7	1118.6	1121.6	1119.6	1126.7	1128.8	1126.7
12.5°	1049.2	1040.0	1017.5	1006.3	994.1	984.9	996.1	987.9	1016.5	1024.7	1047.1
15°	916.5	899.1	883.8	883.8	872.6	864.4	869.6	878.7	884.9	894.0	898.1
17.5°	827.7	820.6	808.3	801.2	798.1	795.0	795.0	799.1	812.4	811.4	819.5
20°	752.2	748.1	742.0	732.8	729.7	727.7	727.7	727.7	736.9	745.0	750.1
22.5°	700.1	697.1	693.0	680.7	674.6	672.6	677.7	680.7	687.9	694.0	699.1
25°	648.1	640.9	633.8	629.7	626.6	626.6	628.7	629.7	632.8	635.8	642.0
27.5°	605.2	600.1	589.9	578.7	578.7	575.6	577.7	579.7	586.8	597.1	602.2
30°	557.2	556.2	552.1	548.1	544.0	541.9	546.0	549.1	550.1	555.2	555.2
32.5°	522.5	515.4	508.3	504.2	502.1	501.1	502.1	506.2	506.2	512.3	519.5
35°	487.8	483.8	476.6	469.5	467.4	462.3	466.4	470.5	477.6	480.7	483.8
37.5°	450.1	445.0	441.9	439.9	435.8	436.8	433.8	439.9	446.0	445.0	447.0
40°	421.5	412.3	403.1	402.1	401.1	400.1	400.1	401.1	405.2	409.3	415.4
42.5°	384.8	381.7	373.5	365.4	363.3	361.3	359.3	363.3	371.5	378.6	381.7
45°	347.0	342.9	340.9	334.8	330.7	329.7	327.6	332.7	339.9	342.9	345.0
47.5°	312.3	311.3	305.2	306.2	303.1	304.1	303.1	306.2	306.2	309.2	311.3
50°	288.8	285.8	282.7	280.7	277.6	277.6	276.6	277.6	281.7	285.8	284.7
52.5°	265.4	260.3	259.2	258.2	256.2	258.2	255.2	256.2	260.3	262.3	261.3
55°	237.8	236.8	234.7	232.7	231.7	230.7	230.7	230.7	234.7	237.8	238.8
57.5°	216.4	211.3	207.2	207.2	203.1	202.1	204.1	205.1	208.2	210.2	212.3
60°	186.8	184.7	178.6	175.5	169.4	168.4	168.4	172.5	177.6	184.7	186.8
62.5°	155.1	152.1	151.0	151.0	151.0	151.0	151.0	151.0	151.0	152.1	152.1
65°	137.8	138.8	137.8	136.8	137.8	137.8	136.8	136.8	136.8	137.8	138.8
67.5°	123.5	122.5	123.5	122.5	121.5	121.5	120.4	121.5	122.5	123.5	123.5
70°	107.2	107.2	106.1	107.2	106.1	105.1	104.1	104.1	106.1	107.2	107.2
72.5°	91.9	91.9	90.8	90.8	88.8	88.8	89.8	88.8	88.8	91.9	91.9
75°	76.5	75.5	74.5	74.5	73.5	73.5	73.5	72.5	74.5	74.5	75.5
77.5°	60.2	60.2	60.2	59.2	59.2	58.2	58.2	59.2	59.2	59.2	60.2
80°	45.9	45.9	45.9	44.9	43.9	43.9	43.9	43.9	43.9	44.9	43.9
82.5°	31.6	31.6	31.6	31.6	31.6	30.6	30.6	30.6	31.6	31.6	30.6
85°	19.4	18.4	19.4	19.4	18.4	19.4	18.4	18.4	17.4	17.4	18.4
87.5°	8.2	7.1	6.1	6.1	7.1	6.1	6.1	6.1	7.1	6.1	6.1
90°	25.0	25.1	25.3	25.4	25.6	25.8	25.6	25.4	25.3	25.1	25.0
92.5°	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3
95°	48.6	48.4	48.1	47.8	47.4	47.1	47.4	47.8	48.1	48.4	48.6
97.5°	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9
100°	104.7	104.6	104.5	104.3	104.2	104.0	104.2	104.3	104.5	104.6	104.7
102.5°	136.6	136.5	136.4	136.2	136.1	135.9	136.1	136.2	136.4	136.5	136.6
105°	168.5	168.5	168.5	168.5	168.5	168.5	168.5	168.5	168.5	168.5	168.5
107.5°	201.9	201.5	200.6	199.8	198.9	198.1	198.9	199.8	200.6	201.5	201.9
110°	236.0	235.8	235.3	234.8	234.3	233.8	234.3	234.8	235.3	235.8	236.0

TEST NUMBER: P1010205

CATALOG NUMBER: S122RDIP-B675D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	269.4	269.2	268.9	268.6	268.2	267.9	268.2	268.6	268.9	269.2	269.4
115°	305.9	305.6	305.1	304.6	304.1	303.6	304.1	304.6	305.1	305.6	305.9
117.5°	339.3	339.0	338.5	338.0	337.5	337.0	337.5	338.0	338.5	339.0	339.3
120°	374.9	374.6	374.1	373.6	373.1	372.6	373.1	373.6	374.1	374.6	374.9
122.5°	409.1	408.9	408.6	408.3	407.9	407.6	407.9	408.3	408.6	408.9	409.1
125°	444.0	443.9	443.7	443.6	443.4	443.2	443.4	443.6	443.7	443.9	444.0
127.5°	477.4	477.1	476.6	476.1	475.6	475.1	475.6	476.1	476.6	477.1	477.4
130°	513.1	512.8	512.1	511.4	510.7	510.0	510.7	511.4	512.1	512.8	513.1
132.5°	545.7	545.4	544.9	544.4	543.9	543.4	543.9	544.4	544.9	545.4	545.7
135°	580.6	580.3	579.8	579.3	578.8	578.3	578.8	579.3	579.8	580.3	580.6
137.5°	612.5	612.2	611.5	610.8	610.1	609.4	610.1	610.8	611.5	612.2	612.5
140°	645.1	644.8	644.1	643.4	642.8	642.1	642.8	643.4	644.1	644.8	645.1
142.5°	674.7	674.4	673.7	673.0	672.4	671.7	672.4	673.0	673.7	674.4	674.7
145°	704.3	704.0	703.3	702.6	702.0	701.3	702.0	702.6	703.3	704.0	704.3
147.5°	730.9	730.6	729.9	729.2	728.5	727.8	728.5	729.2	729.9	730.6	730.9
150°	755.9	755.6	755.1	754.6	754.1	753.6	754.1	754.6	755.1	755.6	755.9
152.5°	781.0	780.7	780.0	779.3	778.6	777.9	778.6	779.3	780.0	780.7	781.0
155°	801.5	801.2	800.7	800.2	799.7	799.2	799.7	800.2	800.7	801.2	801.5
157.5°	821.9	821.5	820.7	819.8	819.0	818.2	819.0	819.8	820.7	821.5	821.9
160°	838.6	838.3	837.6	836.9	836.3	835.6	836.3	836.9	837.6	838.3	838.6
162.5°	854.6	854.2	853.3	852.5	851.6	850.8	851.6	852.5	853.3	854.2	854.6
165°	867.5	867.1	866.2	865.4	864.5	863.7	864.5	865.4	866.2	867.1	867.5
167.5°	878.9	878.5	877.6	876.8	875.9	875.1	875.9	876.8	877.6	878.5	878.9
170°	888.0	887.5	886.5	885.4	884.4	883.4	884.4	885.4	886.5	887.5	888.0
172.5°	894.8	894.3	893.3	892.3	891.3	890.3	891.3	892.3	893.3	894.3	894.8
175°	899.4	898.9	897.9	896.8	895.8	894.8	895.8	896.8	897.9	898.9	899.4
177.5°	901.6	901.1	900.1	899.1	898.1	897.1	898.1	899.1	900.1	901.1	901.6
180°	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4

TEST NUMBER: P1010205

CATALOG NUMBER: S122RDIP-B675D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6	1468.6
2.5°	1399.2	1404.3	1402.3	1391.1	1402.3	1405.4	1411.5	1417.6	1421.7	1427.8	1432.9
5°	1311.5	1321.7	1327.8	1321.7	1342.1	1345.2	1359.4	1367.6	1379.9	1390.1	1398.2
7.5°	1228.8	1237.0	1249.2	1251.3	1263.5	1277.8	1298.2	1318.6	1338.0	1348.2	1357.4
10°	1140.0	1154.3	1172.7	1168.6	1187.0	1209.4	1230.8	1263.5	1279.8	1298.2	1314.5
12.5°	1051.2	1060.4	1084.9	1093.1	1119.6	1136.9	1166.5	1187.0	1227.8	1249.2	1263.5
15°	896.1	933.8	964.5	1001.2	1035.9	1068.6	1095.1	1131.8	1167.6	1183.9	1207.4
17.5°	825.7	843.0	861.4	879.8	924.7	982.8	1029.8	1069.6	1100.2	1121.6	1149.2
20°	752.2	769.5	789.9	807.3	834.9	876.7	934.9	1003.3	1040.0	1062.4	1089.0
22.5°	700.1	716.5	729.7	745.0	766.5	797.1	841.0	925.7	974.7	1002.2	1025.7
25°	644.0	664.4	678.7	689.9	707.3	741.0	776.7	824.6	912.4	933.8	966.5
27.5°	605.2	611.3	627.7	645.0	662.4	680.7	717.5	758.3	817.5	864.4	904.3
30°	559.3	574.6	589.9	597.1	612.4	638.9	661.3	705.2	751.2	787.9	835.9
32.5°	524.6	533.8	544.0	561.3	575.6	594.0	616.4	653.2	692.0	715.4	752.2
35°	485.8	491.9	513.4	520.5	534.8	553.2	575.6	604.2	646.0	664.4	690.9
37.5°	449.1	463.4	469.5	485.8	499.1	517.4	533.8	566.4	594.0	615.4	639.9
40°	420.5	426.6	437.8	452.1	463.4	477.6	498.1	521.5	551.1	568.5	589.9
42.5°	385.8	390.9	405.2	413.3	431.7	445.0	457.2	485.8	512.3	525.6	547.0
45°	348.0	360.3	369.5	385.8	396.0	412.3	427.6	448.0	472.5	487.8	500.1
47.5°	315.4	327.6	336.8	352.1	368.4	375.6	391.9	413.3	435.8	448.0	465.4
50°	288.8	292.9	310.3	317.4	334.8	349.0	360.3	378.6	403.1	410.3	424.6
52.5°	263.3	266.4	277.6	286.8	302.1	314.3	328.6	346.0	366.4	377.6	388.8
55°	240.9	242.9	248.0	258.2	268.4	283.7	297.0	313.3	330.7	342.9	353.1
57.5°	215.3	219.4	223.5	229.6	239.8	254.1	268.4	283.7	298.0	306.2	319.4
60°	185.7	191.9	199.0	206.2	213.3	223.5	239.8	254.1	267.4	274.5	284.7
62.5°	154.1	166.4	172.5	180.6	186.8	196.0	208.2	224.5	233.7	242.9	251.1
65°	138.8	139.8	140.8	149.0	160.2	169.4	180.6	192.9	207.2	213.3	219.4
67.5°	123.5	124.5	126.6	127.6	131.7	141.9	154.1	167.4	178.6	182.7	188.8
70°	108.2	108.2	112.3	113.3	114.3	115.3	125.5	138.8	149.0	154.1	161.3
72.5°	91.9	92.9	94.9	95.9	98.0	100.0	103.1	110.2	122.5	127.6	135.7
75°	75.5	76.5	77.6	78.6	81.6	82.7	85.7	89.8	94.9	101.0	106.1
77.5°	60.2	60.2	61.2	63.3	65.3	66.3	69.4	71.4	73.5	76.5	80.6
80°	44.9	45.9	45.9	48.0	48.0	49.0	50.0	53.1	55.1	57.2	59.2
82.5°	30.6	32.7	32.7	32.7	33.7	34.7	35.7	35.7	37.8	38.8	41.8
85°	18.4	19.4	19.4	19.4	18.4	20.4	20.4	21.4	21.4	21.4	22.5
87.5°	7.1	6.1	7.1	7.1	7.1	8.2	7.1	7.1	8.2	9.2	9.2
90°	25.2	25.5	25.9	26.2	26.6	22.9	19.2	15.5	11.8	9.9	8.9
92.5°	24.2	24.0	23.9	23.7	23.5	23.3	23.2	23.0	22.9	22.8	22.1
95°	48.6	48.6	48.6	48.6	48.6	48.3	47.9	47.6	47.3	47.1	46.3
97.5°	75.9	75.9	75.9	75.9	75.9	75.2	74.6	73.9	73.2	72.9	72.1
100°	104.7	104.7	104.7	104.7	104.7	104.2	103.7	103.2	102.7	102.5	101.8
102.5°	136.5	136.4	136.2	136.1	135.9	135.2	134.5	133.8	133.1	132.8	132.3
105°	168.3	168.0	167.7	167.3	167.0	166.7	166.3	166.0	165.7	165.5	165.2
107.5°	201.8	201.6	201.5	201.3	201.1	201.1	201.1	201.1	201.1	201.1	200.8
110°	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	235.5

TEST NUMBER: P1010205

CATALOG NUMBER: S122RDIP-B675D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	269.7	270.2	270.7	271.2	271.7	271.9	272.1	272.2	272.4	272.5	272.0
115°	306.0	306.1	306.3	306.4	306.6	306.9	307.3	307.6	307.9	308.1	307.6
117.5°	339.5	340.0	340.5	341.0	341.5	342.3	343.2	344.0	344.9	345.3	344.6
120°	374.9	374.9	374.9	374.9	374.9	376.3	377.6	379.0	380.3	381.0	380.3
122.5°	409.4	409.9	410.4	410.9	411.4	412.2	413.0	413.9	414.7	415.1	414.3
125°	444.3	444.8	445.3	445.8	446.3	446.8	447.3	447.8	448.3	448.5	447.7
127.5°	477.7	478.4	479.1	479.7	480.4	481.1	481.8	482.5	483.2	483.5	482.6
130°	513.3	513.6	513.9	514.3	514.6	514.9	515.3	515.6	515.9	516.1	515.0
132.5°	546.1	547.0	547.8	548.7	549.5	549.3	549.1	549.0	548.8	548.7	547.9
135°	580.7	580.9	581.0	581.2	581.4	581.0	580.7	580.3	580.0	579.8	578.9
137.5°	612.6	612.7	612.9	613.0	613.2	612.9	612.5	612.2	611.9	611.7	610.9
140°	645.1	645.1	645.1	645.1	645.1	644.3	643.4	642.6	641.7	641.3	640.5
142.5°	674.6	674.5	674.3	674.2	674.0	673.5	673.0	672.5	672.0	671.7	670.9
145°	704.2	704.1	703.9	703.8	703.6	702.6	701.6	700.5	699.5	699.0	698.4
147.5°	730.7	730.4	730.1	729.7	729.4	728.7	728.0	727.3	726.6	726.3	725.5
150°	755.6	755.1	754.6	754.1	753.6	752.9	752.3	751.6	750.9	750.6	750.1
152.5°	780.7	780.0	779.3	778.6	777.9	777.1	776.2	775.4	774.5	774.1	773.6
155°	801.1	800.2	799.4	798.5	797.7	797.2	796.7	796.2	795.7	795.4	795.1
157.5°	821.3	820.1	819.0	817.8	816.6	816.3	815.9	815.6	815.3	815.1	814.9
160°	838.1	837.1	836.1	835.1	834.1	833.9	833.7	833.6	833.4	833.3	833.1
162.5°	854.0	852.8	851.7	850.5	849.3	849.1	848.9	848.8	848.6	848.5	848.5
165°	866.9	865.7	864.6	863.4	862.2	862.2	862.2	862.2	862.2	862.2	862.3
167.5°	878.3	877.1	876.0	874.8	873.6	873.6	873.6	873.6	873.6	873.6	873.8
170°	887.4	886.2	885.1	883.9	882.7	882.9	883.0	883.2	883.3	883.4	883.7
172.5°	894.2	893.0	891.9	890.7	889.5	889.7	889.9	890.0	890.2	890.3	890.5
175°	898.8	897.6	896.4	895.2	894.0	894.4	894.7	895.1	895.4	895.6	895.8
177.5°	901.1	900.1	899.1	898.1	897.1	897.4	897.8	898.1	898.4	898.6	898.9
180°	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4

TEST NUMBER: P1010205

CATALOG NUMBER: S122RDIP-B675D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1468.6	1468.6	1468.6	1468.6
2.5°	1442.1	1439.0	1457.4	1477.8
5°	1412.5	1417.6	1441.1	1469.7
7.5°	1381.9	1393.1	1420.7	1458.4
10°	1339.0	1359.4	1401.3	1440.1
12.5°	1297.2	1324.7	1364.5	1410.5
15°	1250.2	1280.9	1329.8	1385.0
17.5°	1198.2	1232.9	1290.0	1350.3
20°	1143.1	1189.0	1249.2	1314.5
22.5°	1081.8	1136.9	1199.2	1271.7
25°	1022.6	1082.9	1145.1	1228.8
27.5°	964.5	1023.7	1093.1	1177.8
30°	906.3	960.4	1034.9	1125.7
32.5°	844.0	900.2	978.8	1071.6
35°	786.9	843.0	916.5	1008.4
37.5°	725.6	785.9	856.3	951.2
40°	654.2	724.6	793.0	883.8
42.5°	595.0	669.5	735.9	821.6
45°	548.1	618.5	673.6	757.3
47.5°	504.2	561.3	617.5	695.0
50°	462.3	506.2	564.4	633.8
52.5°	419.5	457.2	507.2	572.6
55°	380.7	416.4	461.3	511.3
57.5°	345.0	370.5	415.4	460.3
60°	305.2	331.7	366.4	404.2
62.5°	271.5	291.9	324.6	356.2
65°	235.8	255.2	279.6	309.2
67.5°	203.1	220.4	239.8	263.3
70°	173.5	186.8	201.1	221.5
72.5°	141.9	156.2	169.4	185.7
75°	116.3	122.5	133.7	144.9
77.5°	89.8	98.0	104.1	113.3
80°	64.3	71.4	73.5	80.6
82.5°	42.9	46.9	51.0	53.1
85°	24.5	26.5	30.6	31.6
87.5°	9.2	10.2	12.2	14.3
90°	6.9	4.8	2.8	0.8
92.5°	20.8	19.4	18.1	16.7
95°	44.6	42.9	41.2	39.5
97.5°	70.6	69.1	67.5	66.0
100°	100.5	99.1	97.8	96.4
102.5°	131.3	130.3	129.3	128.3
105°	164.7	164.2	163.7	163.2
107.5°	200.1	199.4	198.8	198.1
110°	234.5	233.5	232.5	231.5

TEST NUMBER: P1010205

CATALOG NUMBER: S122RDIP-B675D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	271.0	269.9	268.9	267.9
115°	306.6	305.6	304.6	303.6
117.5°	343.3	342.0	340.6	339.3
120°	379.0	377.6	376.3	374.9
122.5°	412.6	410.9	409.3	407.6
125°	446.2	444.7	443.2	441.7
127.5°	480.7	478.8	477.0	475.1
130°	512.8	510.6	508.4	506.2
132.5°	546.2	544.5	542.8	541.1
135°	577.0	575.2	573.3	571.5
137.5°	609.4	607.9	606.4	604.9
140°	639.0	637.5	636.0	634.5
142.5°	669.4	667.9	666.3	664.8
145°	697.2	696.1	694.9	693.7
147.5°	724.0	722.5	721.0	719.5
150°	749.1	748.1	747.1	746.1
152.5°	772.6	771.6	770.6	769.6
155°	794.6	794.1	793.6	793.1
157.5°	814.6	814.3	813.9	813.6
160°	832.8	832.5	832.1	831.8
162.5°	848.5	848.5	848.5	848.5
165°	862.4	862.6	862.7	862.9
167.5°	874.3	874.8	875.3	875.8
170°	884.2	884.7	885.2	885.7
172.5°	891.0	891.5	892.0	892.5
175°	896.3	896.8	897.3	897.8
177.5°	899.4	899.9	900.4	900.9
180°	899.4	899.4	899.4	899.4

(END OF REPORT)