

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010217

Luminaire Tested: S122RDIP-B675D925UB27-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010217
REPORT IS A COMBINATION OF REPORTS P988579 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B675D925UB27-4F0-XX-W2A-A1
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5778.0 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010217

CATALOG NUMBER: S122RDIP-B675D925UB27-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1010217

CATALOG NUMBER: S122RDIP-B675D925UB27-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50
1	97	93	89	86	89	85	82	80	71	69	67	58	56	55	46	45	44
2	89	82	76	72	81	75	71	66	63	60	57	52	49	47	41	39	38
3	82	73	66	60	75	67	61	56	56	52	48	46	43	41	37	35	33
4	75	65	58	52	69	60	53	48	51	46	42	42	38	36	34	31	29
5	69	58	51	45	63	54	47	42	46	41	37	38	34	31	31	28	26
6	64	53	45	39	59	49	42	37	41	36	32	35	31	28	28	26	23
7	59	48	40	35	54	44	38	33	38	33	29	32	28	25	26	23	21
8	55	44	36	31	51	40	34	29	35	30	26	29	25	23	24	21	19
9	52	40	33	28	47	37	31	26	32	27	23	27	23	21	22	20	18
10	48	37	30	25	44	34	28	24	30	25	21	25	21	19	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23174	23174	23174	23174
5°	23228	24614	23309	19664
10°	22972	26017	23135	16239
15°	22474	26025	22855	12199
20°	21875	21513	22351	10065
25°	21147	13443	21605	8562
30°	20220	8607	20769	7371
35°	19090	6615	19708	6308
40°	17833	5560	18594	5517
45°	16487	4732	17175	4632
50°	15109	4020	15814	4006
55°	13582	3495	14314	3448
60°	12226	2664	12872	2633
65°	10960	2006	11610	2274
70°	9562	1601	10311	1854
75°	8083	1227	8822	1403
80°	6419	835	6906	919
85°	4450	430	4887	454

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 21199 cd/sqm

TEST NUMBER: P1010217

CATALOG NUMBER: S122RDIP-B675D925UB27-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.9	2.4
10°-20°	387.6	6.7
20°-30°	498.8	8.6
30°-40°	473.3	8.2
40°-50°	405.6	7.0
50°-60°	308.9	5.3
60°-70°	194.8	3.4
70°-80°	97.2	1.7
80°-90°	28.3	0.5
90°-100°	71.8	1.2
100°-110°	228.2	4.0
110°-120°	390.5	6.8
120°-130°	513.6	8.9
130°-140°	576.5	10.0
140°-150°	565.4	9.8
150°-160°	474.2	8.2
160°-170°	314.5	5.4
170°-180°	109.9	1.9
0°-30°	1025.3	17.7
0°-40°	1498.6	25.9
0°-60°	2213.0	38.3
0°-90°	2533.3	43.8
90°-120°	690.5	12.0
90°-150°	2346.0	40.6
90°-180°	3245.0	56.2
0°-180°	5778.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1464	1464	1464	1464	1464	
5°	1465	1629	1470	1301	1465	139
15°	1381	1838	1404	862	1381	388
25°	1225	981	1251	625	1225	562
35°	1005	483	1038	461	1005	629
45°	755	336	786	329	755	583
55°	510	233	537	230	510	459
65°	308	121	327	137	308	306
75°	144	64	158	73	144	156
85°	32	18	35	19	32	36
90°	1	33	1	33	1	5
95°	51	61	51	61	51	57
105°	211	217	211	217	211	222
115°	392	392	392	392	392	388
125°	570	572	570	572	570	509
135°	738	746	738	746	738	570
145°	895	905	895	905	895	559
155°	1023	1031	1023	1031	1023	471
165°	1114	1114	1114	1114	1114	314
175°	1159	1155	1159	1155	1159	110
180°	1161	1161	1161	1161	1161	

TEST NUMBER: P1010217

CATALOG NUMBER: S122RDIP-B675D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1473.2	1479.3	1482.3	1486.4	1495.6	1501.7	1510.8	1512.8	1511.8	1515.9	1504.7
5°	1465.0	1478.3	1490.5	1500.6	1516.9	1527.1	1538.3	1551.5	1554.6	1569.8	1560.7
7.5°	1453.8	1473.2	1490.5	1510.8	1535.2	1548.5	1565.8	1586.1	1595.3	1613.6	1618.7
10°	1435.5	1463.0	1492.5	1513.9	1547.4	1570.8	1587.1	1619.7	1641.0	1668.5	1664.4
12.5°	1406.0	1441.6	1481.3	1516.9	1560.7	1575.9	1606.4	1640.0	1667.5	1692.9	1715.3
15°	1380.6	1421.3	1465.0	1508.8	1558.6	1587.1	1617.6	1661.4	1690.9	1735.7	1755.0
17.5°	1346.0	1397.9	1449.8	1498.6	1557.6	1590.2	1627.8	1670.5	1714.3	1757.0	1772.3
20°	1310.4	1366.3	1422.3	1488.4	1555.6	1587.1	1625.8	1678.7	1721.4	1755.0	1755.0
22.5°	1267.7	1335.8	1399.9	1463.0	1536.2	1582.0	1621.7	1683.8	1714.3	1721.4	1693.9
25°	1224.9	1293.1	1363.3	1441.6	1525.1	1565.8	1610.5	1668.5	1678.7	1650.2	1579.0
27.5°	1174.1	1250.4	1329.7	1414.2	1501.7	1552.5	1593.2	1631.9	1612.6	1536.2	1425.4
30°	1122.2	1204.6	1294.1	1374.5	1480.3	1527.1	1561.7	1572.9	1511.8	1387.7	1244.3
32.5°	1068.3	1148.6	1243.2	1339.9	1446.7	1491.5	1513.9	1484.4	1372.5	1215.8	1040.8
35°	1005.2	1095.7	1194.4	1295.1	1400.9	1434.5	1447.7	1375.5	1232.1	1029.6	855.6
37.5°	948.2	1038.7	1144.6	1247.3	1350.1	1368.4	1355.2	1242.2	1060.1	859.7	689.8
40°	881.1	977.7	1081.5	1196.4	1280.9	1286.0	1253.4	1106.9	881.1	692.8	588.0
42.5°	819.0	916.7	1020.4	1137.4	1201.5	1184.2	1140.5	948.2	735.6	597.2	512.8
45°	754.9	847.5	959.4	1063.2	1108.9	1068.3	1002.1	797.6	617.6	513.8	448.7
47.5°	692.8	779.3	890.2	989.9	998.1	952.3	873.9	668.4	535.1	451.7	398.8
50°	631.8	718.3	822.0	904.5	896.3	833.2	744.7	580.9	464.9	398.8	355.1
52.5°	570.8	649.1	749.8	814.9	780.3	719.3	631.8	492.4	405.9	347.9	314.4
55°	509.7	583.0	669.4	723.4	668.4	598.2	536.2	422.2	352.0	305.2	279.8
57.5°	458.8	516.8	596.2	628.7	562.6	507.7	453.8	363.2	305.2	271.6	242.1
60°	402.9	455.8	520.9	540.2	472.1	427.3	381.5	307.2	261.5	232.0	212.6
62.5°	355.1	398.8	448.7	448.7	388.6	355.1	320.5	257.4	219.8	196.4	187.2
65°	308.3	339.8	375.4	371.3	320.5	291.0	263.5	212.6	184.1	167.9	158.7
67.5°	262.5	286.9	310.3	296.1	259.4	234.0	208.6	171.9	152.6	141.4	129.2
70°	220.8	240.1	252.3	239.1	202.5	181.1	162.8	138.4	123.1	108.9	101.7
72.5°	185.2	193.3	197.4	181.1	150.6	138.4	125.1	107.8	94.6	87.5	85.5
75°	144.5	151.6	148.5	136.3	110.9	101.7	91.6	79.4	76.3	72.2	70.2
77.5°	112.9	112.9	107.8	96.7	79.4	72.2	68.2	62.1	59.0	58.0	56.0
80°	80.4	79.4	76.3	64.1	53.9	49.9	49.9	45.8	44.8	42.7	42.7
82.5°	52.9	52.9	48.8	38.7	35.6	34.6	33.6	31.5	31.5	30.5	30.5
85°	31.5	29.5	24.4	21.4	20.3	20.3	19.3	18.3	19.3	18.3	18.3
87.5°	14.2	11.2	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
90°	1.0	3.6	6.2	8.8	11.4	12.7	15.1	19.9	24.7	29.5	34.3
92.5°	21.5	23.3	25.0	26.8	28.5	29.4	29.5	29.7	30.0	30.2	30.4
95°	50.9	53.1	55.3	57.4	59.6	60.7	60.9	61.4	61.8	62.3	62.7
97.5°	85.2	87.2	89.1	91.1	93.0	94.0	94.4	95.3	96.2	97.0	97.9
100°	124.4	126.1	127.9	129.6	131.3	132.2	132.5	133.2	133.9	134.5	135.2
102.5°	165.5	166.8	168.1	169.4	170.7	171.4	171.8	172.7	173.6	174.4	175.3
105°	210.6	211.2	211.9	212.5	213.2	213.5	213.7	214.2	214.6	215.1	215.5
107.5°	255.6	256.5	257.3	258.2	259.1	259.5	259.5	259.5	259.5	259.5	259.5
110°	298.7	300.0	301.3	302.6	303.9	304.6	304.6	304.6	304.6	304.6	304.6



TEST NUMBER: P1010217

CATALOG NUMBER: S122RDIP-B675D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	345.7	347.0	348.3	349.6	350.9	351.6	351.5	351.3	351.0	350.8	350.6
115°	391.7	393.0	394.3	395.6	396.9	397.6	397.4	397.0	396.5	396.1	395.7
117.5°	437.8	439.5	441.3	443.0	444.7	445.6	445.1	444.0	442.9	441.8	440.7
120°	483.8	485.5	487.3	489.0	490.7	491.6	490.7	489.0	487.3	485.5	483.8
122.5°	525.9	528.1	530.3	532.4	534.6	535.7	535.2	534.1	533.0	531.9	530.8
125°	570.0	572.0	573.9	575.9	577.8	578.8	578.5	577.8	577.2	576.5	575.9
127.5°	613.1	615.5	617.9	620.3	622.7	623.9	623.5	622.6	621.7	620.8	619.9
130°	653.2	656.0	658.9	661.7	664.6	666.0	665.8	665.3	664.9	664.4	664.0
132.5°	698.3	700.5	702.7	704.8	707.0	708.1	708.2	708.4	708.7	708.9	709.1
135°	737.5	739.9	742.3	744.6	747.0	748.2	748.4	748.9	749.3	749.8	750.2
137.5°	780.6	782.6	784.5	786.5	788.4	789.4	789.6	790.0	790.5	790.9	791.3
140°	818.8	820.8	822.7	824.7	826.6	827.6	828.1	829.2	830.3	831.4	832.5
142.5°	857.9	859.9	861.8	863.8	865.7	866.7	867.0	867.7	868.4	869.0	869.7
145°	895.1	896.6	898.2	899.7	901.2	902.0	902.7	904.0	905.3	906.6	907.9
147.5°	928.4	930.4	932.4	934.3	936.3	937.3	937.7	938.6	939.5	940.3	941.2
150°	962.7	964.0	965.3	966.6	967.9	968.6	969.0	969.9	970.8	971.6	972.5
152.5°	993.1	994.4	995.7	997.0	998.3	999.0	999.5	1000.6	1001.7	1002.8	1003.9
155°	1023.4	1024.1	1024.7	1025.4	1026.1	1026.4	1026.7	1027.4	1028.0	1028.7	1029.3
157.5°	1049.9	1050.3	1050.7	1051.2	1051.6	1051.8	1052.0	1052.5	1052.9	1053.4	1053.8
160°	1073.4	1073.8	1074.3	1074.7	1075.2	1075.4	1075.5	1075.7	1075.9	1076.1	1076.3
162.5°	1094.9	1094.9	1094.9	1094.9	1094.9	1094.9	1095.0	1095.2	1095.5	1095.7	1095.9
165°	1113.5	1113.3	1113.1	1112.9	1112.7	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
167.5°	1130.2	1129.6	1128.9	1128.3	1127.6	1127.3	1127.3	1127.3	1127.3	1127.3	1127.3
170°	1142.9	1142.3	1141.6	1141.0	1140.3	1140.0	1139.9	1139.7	1139.4	1139.2	1139.0
172.5°	1151.7	1151.1	1150.4	1149.8	1149.1	1148.8	1148.7	1148.5	1148.2	1148.0	1147.8
175°	1158.6	1158.0	1157.3	1156.7	1156.0	1155.7	1155.5	1155.0	1154.6	1154.1	1153.7
177.5°	1162.5	1161.9	1161.2	1160.6	1159.9	1159.6	1159.4	1158.9	1158.5	1158.0	1157.6
180°	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6

TEST NUMBER: P1010217

CATALOG NUMBER: S122RDIP-B675D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1515.9	1517.9	1521.0	1535.2	1537.3	1541.3	1539.3	1539.3	1540.3	1538.3	1539.3
5°	1581.0	1584.1	1599.3	1616.6	1620.7	1616.6	1621.7	1628.8	1628.8	1628.8	1626.8
7.5°	1642.1	1653.2	1670.5	1696.0	1701.1	1706.2	1715.3	1709.2	1711.2	1720.4	1717.3
10°	1701.1	1717.3	1736.7	1758.0	1769.2	1776.4	1780.4	1789.6	1810.9	1786.5	1795.7
12.5°	1757.0	1780.4	1800.8	1824.2	1832.3	1841.5	1844.5	1852.7	1852.7	1851.6	1858.8
15°	1793.6	1815.0	1833.3	1848.6	1850.6	1848.6	1846.6	1847.6	1850.6	1838.4	1845.5
17.5°	1801.8	1803.8	1809.9	1803.8	1804.8	1783.5	1771.3	1768.2	1739.7	1740.7	1764.1
20°	1762.1	1727.5	1718.4	1684.8	1664.4	1609.5	1607.5	1592.2	1532.2	1550.5	1546.4
22.5°	1653.2	1594.2	1515.9	1477.2	1457.9	1399.9	1355.2	1323.6	1302.3	1280.9	1271.7
25°	1509.8	1414.2	1303.3	1227.0	1215.8	1161.9	1079.4	1040.8	995.0	980.8	1005.2
27.5°	1324.6	1200.5	1075.4	958.4	937.0	888.2	846.5	819.0	766.1	763.0	765.1
30°	1073.3	948.2	843.4	767.1	714.2	691.8	664.4	644.0	622.6	630.8	632.8
32.5°	882.1	763.0	665.4	624.7	600.3	586.0	562.6	549.4	540.2	537.2	536.2
35°	701.0	621.6	577.9	538.2	524.0	513.8	496.5	490.4	482.2	483.3	483.3
37.5°	600.3	534.1	501.6	481.2	468.0	462.9	451.7	445.6	440.5	438.5	441.5
40°	517.8	472.1	451.7	433.4	422.2	420.2	414.1	407.0	400.8	401.9	404.9
42.5°	457.8	431.4	407.0	392.7	384.6	381.5	376.4	371.3	371.3	368.3	367.3
45°	410.0	388.6	368.3	355.1	350.0	345.9	339.8	338.8	334.7	335.7	336.8
47.5°	367.3	350.0	334.7	321.5	316.4	315.4	309.3	305.2	305.2	304.2	303.2
50°	328.6	311.3	298.1	291.0	283.9	281.8	280.8	279.8	277.7	277.7	278.8
52.5°	297.1	279.8	269.6	263.5	259.4	257.4	257.4	256.4	256.4	256.4	255.4
55°	262.5	248.2	240.1	238.1	236.0	235.0	234.0	232.0	230.9	233.0	230.9
57.5°	229.9	224.8	217.7	215.7	210.6	210.6	207.5	205.5	203.5	205.5	205.5
60°	204.5	197.4	193.3	187.2	183.1	179.1	174.0	173.0	170.9	169.9	168.9
62.5°	178.0	171.9	161.8	152.6	146.5	142.4	140.4	139.4	139.4	138.4	138.4
65°	148.5	134.3	129.2	126.2	125.1	124.1	122.1	121.1	122.1	121.1	122.1
67.5°	116.0	113.9	110.9	108.9	107.8	106.8	106.8	105.8	105.8	105.8	105.8
70°	100.7	95.6	94.6	92.6	92.6	91.6	91.6	91.6	91.6	90.5	92.6
72.5°	83.4	80.4	79.4	78.3	78.3	78.3	77.3	77.3	77.3	76.3	77.3
75°	68.2	67.1	65.1	65.1	64.1	65.1	64.1	64.1	63.1	64.1	64.1
77.5°	54.9	53.9	52.9	52.9	51.9	51.9	51.9	51.9	51.9	51.9	52.9
80°	41.7	40.7	39.7	40.7	39.7	40.7	39.7	39.7	40.7	39.7	39.7
82.5°	30.5	29.5	29.5	28.5	28.5	28.5	28.5	28.5	28.5	28.5	28.5
85°	18.3	17.3	17.3	18.3	17.3	18.3	17.3	17.3	17.3	18.3	18.3
87.5°	8.1	9.2	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	9.2
90°	33.9	33.4	33.0	32.5	32.3	32.4	32.6	32.9	33.1	33.3	33.1
92.5°	30.6	30.8	31.0	31.2	31.3	31.3	31.3	31.3	31.3	31.3	31.3
95°	62.7	62.7	62.7	62.7	62.7	62.5	62.0	61.6	61.1	60.7	61.1
97.5°	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9
100°	135.2	135.2	135.2	135.2	135.2	135.1	134.9	134.6	134.4	134.2	134.4
102.5°	175.5	175.7	176.0	176.2	176.3	176.2	176.0	175.7	175.5	175.3	175.5
105°	215.9	216.3	216.8	217.2	217.4	217.4	217.4	217.4	217.4	217.4	217.4
107.5°	259.7	259.9	260.2	260.4	260.5	260.0	258.9	257.8	256.7	255.6	256.7
110°	304.6	304.6	304.6	304.6	304.6	304.3	303.6	302.9	302.3	301.6	302.3

TEST NUMBER: P1010217

CATALOG NUMBER: S122RDIP-B675D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	350.0	349.3	348.7	348.0	347.7	347.5	347.0	346.6	346.1	345.7	346.1
115°	395.5	395.3	395.0	394.8	394.7	394.4	393.7	393.0	392.4	391.7	392.4
117.5°	440.1	439.4	438.8	438.1	437.8	437.5	436.8	436.1	435.5	434.8	435.5
120°	483.8	483.8	483.8	483.8	483.8	483.5	482.8	482.2	481.5	480.9	481.5
122.5°	530.2	529.5	528.9	528.2	527.9	527.7	527.2	526.8	526.3	525.9	526.3
125°	575.2	574.6	573.9	573.2	572.9	572.8	572.6	572.4	572.2	572.0	572.2
127.5°	619.0	618.2	617.3	616.4	616.0	615.7	615.0	614.4	613.7	613.1	613.7
130°	663.6	663.2	662.7	662.3	662.1	661.7	660.8	659.9	659.0	658.1	659.0
132.5°	708.0	706.9	705.8	704.7	704.2	703.9	703.2	702.5	701.9	701.2	701.9
135°	750.0	749.8	749.5	749.3	749.2	748.9	748.2	747.6	746.9	746.3	746.9
137.5°	791.1	790.9	790.7	790.5	790.4	790.0	789.1	788.2	787.3	786.4	787.3
140°	832.5	832.5	832.5	832.5	832.5	832.1	831.2	830.3	829.4	828.5	829.4
142.5°	869.9	870.1	870.4	870.6	870.7	870.3	869.4	868.5	867.6	866.7	867.6
145°	908.1	908.3	908.6	908.8	908.9	908.5	907.6	906.7	905.8	904.9	905.8
147.5°	941.6	942.0	942.5	942.9	943.1	942.7	941.8	940.9	940.1	939.2	940.1
150°	973.2	973.8	974.5	975.2	975.5	975.2	974.5	973.8	973.2	972.5	973.2
152.5°	1004.8	1005.6	1006.5	1007.4	1007.8	1007.4	1006.5	1005.6	1004.8	1003.9	1004.8
155°	1030.4	1031.5	1032.6	1033.7	1034.2	1033.9	1033.2	1032.6	1031.9	1031.3	1031.9
157.5°	1055.3	1056.9	1058.4	1059.9	1060.7	1060.2	1059.1	1058.0	1056.9	1055.8	1056.9
160°	1077.6	1078.9	1080.2	1081.5	1082.2	1081.8	1080.9	1080.0	1079.2	1078.3	1079.2
162.5°	1097.4	1099.0	1100.5	1102.0	1102.8	1102.3	1101.2	1100.1	1099.0	1097.9	1099.0
165°	1114.1	1115.6	1117.1	1118.6	1119.4	1118.9	1117.8	1116.7	1115.6	1114.5	1115.6
167.5°	1128.8	1130.3	1131.8	1133.3	1134.1	1133.6	1132.5	1131.4	1130.3	1129.2	1130.3
170°	1140.5	1142.1	1143.6	1145.1	1145.9	1145.2	1143.9	1142.6	1141.3	1140.0	1141.3
172.5°	1149.3	1150.9	1152.4	1153.9	1154.7	1154.0	1152.7	1151.4	1150.1	1148.8	1150.1
175°	1155.2	1156.8	1158.3	1159.8	1160.6	1159.9	1158.6	1157.3	1156.0	1154.7	1156.0
177.5°	1158.9	1160.2	1161.5	1162.8	1163.5	1162.8	1161.5	1160.2	1158.9	1157.6	1158.9
180°	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6

TEST NUMBER: P1010217

CATALOG NUMBER: S122RDIP-B675D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1543.4	1536.2	1534.2	1536.2	1534.2	1535.2	1528.1	1501.7	1508.8	1497.6	1503.7
5°	1630.9	1624.8	1611.5	1609.5	1607.5	1605.4	1595.3	1571.9	1562.7	1547.4	1546.4
7.5°	1714.3	1714.3	1704.1	1697.0	1687.8	1680.7	1667.5	1632.9	1618.7	1600.3	1590.2
10°	1796.7	1770.2	1781.4	1774.3	1751.9	1747.9	1723.4	1703.1	1675.6	1657.3	1641.0
12.5°	1855.7	1847.6	1837.4	1831.3	1825.2	1812.0	1795.7	1743.8	1729.6	1692.9	1674.6
15°	1853.7	1848.6	1851.6	1851.6	1849.6	1846.6	1833.3	1795.7	1771.3	1735.7	1704.1
17.5°	1754.0	1767.2	1780.4	1789.6	1809.9	1819.1	1831.3	1808.9	1793.6	1763.1	1729.6
20°	1580.0	1612.6	1651.2	1659.4	1677.7	1731.6	1756.0	1775.3	1781.4	1771.3	1743.8
22.5°	1337.9	1365.3	1458.9	1456.9	1483.3	1547.4	1618.7	1676.6	1722.4	1747.9	1737.7
25°	1047.9	1086.6	1136.4	1174.1	1260.5	1356.2	1444.7	1537.3	1616.6	1686.8	1704.1
27.5°	792.5	843.4	883.1	932.9	976.7	1089.6	1203.6	1348.0	1440.6	1573.9	1643.1
30°	641.0	664.4	704.0	727.4	748.8	835.3	964.5	1106.9	1269.7	1423.3	1542.4
32.5°	547.4	563.6	593.1	603.3	625.7	683.7	765.1	895.3	1063.2	1249.3	1406.0
35°	491.4	508.7	514.8	524.0	542.3	578.9	634.8	729.5	881.1	1063.2	1250.4
37.5°	443.6	452.7	470.0	476.1	482.2	509.7	547.4	613.5	714.2	863.8	1071.3
40°	410.0	415.1	424.2	429.3	433.4	452.7	486.3	531.1	605.3	719.3	910.6
42.5°	374.4	380.5	386.6	392.7	397.8	413.1	433.4	476.1	526.0	612.5	750.8
45°	339.8	343.9	351.0	355.1	362.2	374.4	392.7	422.2	467.0	521.9	633.8
47.5°	308.3	313.4	316.4	321.5	326.6	339.8	357.1	376.4	413.1	467.0	548.4
50°	279.8	285.9	290.0	291.0	295.0	307.2	321.5	342.9	366.3	408.0	479.2
52.5°	259.4	260.5	263.5	267.6	266.6	273.7	286.9	303.2	327.6	361.2	413.1
55°	236.0	239.1	241.1	242.1	242.1	248.2	255.4	270.6	290.0	317.4	361.2
57.5°	206.5	209.6	215.7	217.7	220.8	223.8	226.9	237.1	253.3	279.8	315.4
60°	176.0	178.0	184.1	188.2	190.3	198.4	202.5	210.6	219.8	239.1	272.7
62.5°	141.4	143.5	146.5	150.6	154.6	166.9	177.0	185.2	192.3	205.5	233.0
65°	123.1	124.1	126.2	127.2	128.2	133.3	142.4	153.6	166.9	177.0	193.3
67.5°	106.8	107.8	108.9	110.9	111.9	112.9	117.0	120.1	133.3	147.5	159.7
70°	91.6	93.6	94.6	94.6	95.6	97.7	99.7	103.8	107.8	115.0	130.2
72.5°	77.3	78.3	80.4	80.4	80.4	82.4	84.4	86.5	88.5	92.6	98.7
75°	64.1	66.1	66.1	66.1	67.1	67.1	69.2	71.2	73.3	76.3	78.3
77.5°	52.9	52.9	52.9	52.9	53.9	53.9	54.9	57.0	58.0	59.0	61.0
80°	39.7	40.7	40.7	40.7	41.7	41.7	41.7	43.7	44.8	44.8	46.8
82.5°	29.5	29.5	29.5	30.5	29.5	30.5	30.5	31.5	30.5	31.5	32.6
85°	18.3	18.3	18.3	19.3	19.3	19.3	19.3	19.3	19.3	19.3	20.3
87.5°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	10.2	9.2	9.2
90°	32.9	32.6	32.4	32.3	32.5	33.0	33.4	33.9	34.3	29.5	24.7
92.5°	31.3	31.3	31.3	31.3	31.2	31.0	30.8	30.6	30.4	30.2	30.0
95°	61.6	62.0	62.5	62.7	62.7	62.7	62.7	62.7	62.7	62.3	61.8
97.5°	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.0	96.2
100°	134.6	134.9	135.1	135.2	135.2	135.2	135.2	135.2	135.2	134.5	133.9
102.5°	175.7	176.0	176.2	176.3	176.2	176.0	175.7	175.5	175.3	174.4	173.6
105°	217.4	217.4	217.4	217.4	217.2	216.8	216.3	215.9	215.5	215.1	214.6
107.5°	257.8	258.9	260.0	260.5	260.4	260.2	259.9	259.7	259.5	259.5	259.5
110°	302.9	303.6	304.3	304.6	304.6	304.6	304.6	304.6	304.6	304.6	304.6

TEST NUMBER: P1010217

CATALOG NUMBER: S122RDIP-B675D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	346.6	347.0	347.5	347.7	348.0	348.7	349.3	350.0	350.6	350.8	351.0
115°	393.0	393.7	394.4	394.7	394.8	395.0	395.3	395.5	395.7	396.1	396.5
117.5°	436.1	436.8	437.5	437.8	438.1	438.8	439.4	440.1	440.7	441.8	442.9
120°	482.2	482.8	483.5	483.8	483.8	483.8	483.8	483.8	483.8	485.5	487.3
122.5°	526.8	527.2	527.7	527.9	528.2	528.9	529.5	530.2	530.8	531.9	533.0
125°	572.4	572.6	572.8	572.9	573.2	573.9	574.6	575.2	575.9	576.5	577.2
127.5°	614.4	615.0	615.7	616.0	616.4	617.3	618.2	619.0	619.9	620.8	621.7
130°	659.9	660.8	661.7	662.1	662.3	662.7	663.2	663.6	664.0	664.4	664.9
132.5°	702.5	703.2	703.9	704.2	704.7	705.8	706.9	708.0	709.1	708.9	708.7
135°	747.6	748.2	748.9	749.2	749.3	749.5	749.8	750.0	750.2	749.8	749.3
137.5°	788.2	789.1	790.0	790.4	790.5	790.7	790.9	791.1	791.3	790.9	790.5
140°	830.3	831.2	832.1	832.5	832.5	832.5	832.5	832.5	832.5	831.4	830.3
142.5°	868.5	869.4	870.3	870.7	870.6	870.4	870.1	869.9	869.7	869.0	868.4
145°	906.7	907.6	908.5	908.9	908.8	908.6	908.3	908.1	907.9	906.6	905.3
147.5°	940.9	941.8	942.7	943.1	942.9	942.5	942.0	941.6	941.2	940.3	939.5
150°	973.8	974.5	975.2	975.5	975.2	974.5	973.8	973.2	972.5	971.6	970.8
152.5°	1005.6	1006.5	1007.4	1007.8	1007.4	1006.5	1005.6	1004.8	1003.9	1002.8	1001.7
155°	1032.6	1033.2	1033.9	1034.2	1033.7	1032.6	1031.5	1030.4	1029.3	1028.7	1028.0
157.5°	1058.0	1059.1	1060.2	1060.7	1059.9	1058.4	1056.9	1055.3	1053.8	1053.4	1052.9
160°	1080.0	1080.9	1081.8	1082.2	1081.5	1080.2	1078.9	1077.6	1076.3	1076.1	1075.9
162.5°	1100.1	1101.2	1102.3	1102.8	1102.0	1100.5	1099.0	1097.4	1095.9	1095.7	1095.5
165°	1116.7	1117.8	1118.9	1119.4	1118.6	1117.1	1115.6	1114.1	1112.6	1112.6	1112.6
167.5°	1131.4	1132.5	1133.6	1134.1	1133.3	1131.8	1130.3	1128.8	1127.3	1127.3	1127.3
170°	1142.6	1143.9	1145.2	1145.9	1145.1	1143.6	1142.1	1140.5	1139.0	1139.2	1139.4
172.5°	1151.4	1152.7	1154.0	1154.7	1153.9	1152.4	1150.9	1149.3	1147.8	1148.0	1148.2
175°	1157.3	1158.6	1159.9	1160.6	1159.8	1158.3	1156.8	1155.2	1153.7	1154.1	1154.6
177.5°	1160.2	1161.5	1162.8	1163.5	1162.8	1161.5	1160.2	1158.9	1157.6	1158.0	1158.5
180°	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6

TEST NUMBER: P1010217

CATALOG NUMBER: S122RDIP-B675D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1494.5	1489.4	1489.4	1486.4	1486.4	1470.1	1470.1	1475.2	1469.1	1462.0	1451.8
5°	1533.2	1522.0	1519.0	1514.9	1501.7	1481.3	1473.2	1470.1	1457.9	1442.7	1425.4
7.5°	1569.8	1551.5	1542.4	1533.2	1515.9	1487.4	1471.1	1459.9	1441.6	1418.2	1395.9
10°	1605.4	1582.0	1558.6	1547.4	1523.0	1487.4	1464.0	1445.7	1419.3	1387.7	1356.2
12.5°	1638.0	1589.2	1585.1	1562.7	1527.1	1486.4	1450.8	1424.3	1390.8	1354.1	1317.5
15°	1666.5	1616.6	1592.2	1571.9	1525.1	1474.2	1436.5	1404.0	1359.2	1317.5	1272.7
17.5°	1680.7	1626.8	1610.5	1576.9	1529.1	1463.0	1412.1	1372.5	1323.6	1273.8	1222.9
20°	1695.0	1631.9	1605.4	1582.0	1516.9	1441.6	1384.7	1338.9	1285.0	1225.9	1170.0
22.5°	1702.1	1631.9	1600.3	1567.8	1504.7	1418.2	1351.1	1297.2	1234.1	1174.1	1106.9
25°	1689.9	1625.8	1588.1	1554.6	1483.3	1389.7	1312.4	1251.4	1184.2	1116.1	1047.9
27.5°	1659.4	1611.5	1567.8	1533.2	1453.8	1353.1	1271.7	1202.5	1133.4	1057.1	987.9
30°	1602.4	1581.0	1546.4	1507.8	1421.3	1320.6	1223.9	1152.7	1076.4	1000.1	927.9
32.5°	1513.9	1532.2	1509.8	1476.2	1382.6	1275.8	1173.0	1100.8	1017.4	935.0	868.8
35°	1406.0	1471.1	1458.9	1435.5	1341.9	1228.0	1125.2	1037.7	954.3	870.9	804.8
37.5°	1288.0	1386.7	1396.9	1382.6	1295.1	1179.1	1066.2	980.8	895.3	810.9	743.7
40°	1126.2	1277.8	1310.4	1316.5	1246.3	1120.1	1002.1	918.7	834.3	751.8	670.5
42.5°	977.7	1169.0	1209.7	1235.1	1184.2	1062.1	943.1	850.5	767.1	692.8	611.4
45°	838.3	1037.7	1103.9	1136.4	1114.0	996.0	872.9	786.4	710.1	642.0	563.6
47.5°	694.9	895.3	987.9	1039.8	1039.8	928.9	805.8	720.3	647.1	589.1	519.9
50°	599.2	766.1	861.7	929.9	948.2	860.7	744.7	661.3	592.1	529.0	476.1
52.5°	510.7	660.3	739.6	810.9	863.8	787.5	676.6	601.3	533.1	474.1	432.4
55°	441.5	553.5	625.7	704.0	763.0	713.2	610.4	537.2	478.2	429.3	393.7
57.5°	375.4	473.1	532.1	601.3	664.4	626.7	544.3	481.2	429.3	386.6	355.1
60°	319.5	398.8	444.6	498.5	576.9	550.4	482.2	424.2	382.5	343.9	317.4
62.5°	271.6	334.7	373.4	412.0	483.3	471.0	418.1	373.4	337.8	305.2	282.8
65°	222.8	274.7	305.2	338.8	395.8	400.8	358.1	326.6	294.0	265.5	245.2
67.5°	180.1	220.8	248.2	276.7	322.5	336.8	307.2	280.8	253.3	229.9	211.6
70°	145.5	174.0	194.3	216.7	254.3	271.6	256.4	238.1	215.7	196.4	180.1
72.5°	115.0	133.3	145.5	162.8	193.3	210.6	209.6	193.3	177.0	163.8	150.6
75°	84.4	98.7	108.9	120.1	144.5	160.7	164.8	157.7	141.4	131.2	121.1
77.5°	64.1	72.2	77.3	85.5	102.8	117.0	123.1	121.1	109.9	101.7	94.6
80°	48.8	50.9	52.9	56.0	70.2	83.4	87.5	86.5	80.4	77.3	69.2
82.5°	34.6	35.6	36.6	37.6	42.7	53.9	58.0	60.0	54.9	51.9	44.8
85°	20.3	21.4	21.4	23.4	24.4	27.5	34.6	34.6	33.6	29.5	28.5
87.5°	10.2	10.2	9.2	9.2	10.2	11.2	13.2	15.3	13.2	12.2	11.2
90°	19.9	15.1	12.7	11.4	8.8	6.2	3.6	1.0	3.6	6.2	8.8
92.5°	29.7	29.5	29.4	28.5	26.8	25.0	23.3	21.5	23.3	25.0	26.8
95°	61.4	60.9	60.7	59.6	57.4	55.3	53.1	50.9	53.1	55.3	57.4
97.5°	95.3	94.4	94.0	93.0	91.1	89.1	87.2	85.2	87.2	89.1	91.1
100°	133.2	132.5	132.2	131.3	129.6	127.9	126.1	124.4	126.1	127.9	129.6
102.5°	172.7	171.8	171.4	170.7	169.4	168.1	166.8	165.5	166.8	168.1	169.4
105°	214.2	213.7	213.5	213.2	212.5	211.9	211.2	210.6	211.2	211.9	212.5
107.5°	259.5	259.5	259.5	259.1	258.2	257.3	256.5	255.6	256.5	257.3	258.2
110°	304.6	304.6	304.6	303.9	302.6	301.3	300.0	298.7	300.0	301.3	302.6

TEST NUMBER: P1010217

CATALOG NUMBER: S122RDIP-B675D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	351.3	351.5	351.6	350.9	349.6	348.3	347.0	345.7	347.0	348.3	349.6
115°	397.0	397.4	397.6	396.9	395.6	394.3	393.0	391.7	393.0	394.3	395.6
117.5°	444.0	445.1	445.6	444.7	443.0	441.3	439.5	437.8	439.5	441.3	443.0
120°	489.0	490.7	491.6	490.7	489.0	487.3	485.5	483.8	485.5	487.3	489.0
122.5°	534.1	535.2	535.7	534.6	532.4	530.3	528.1	525.9	528.1	530.3	532.4
125°	577.8	578.5	578.8	577.8	575.9	573.9	572.0	570.0	572.0	573.9	575.9
127.5°	622.6	623.5	623.9	622.7	620.3	617.9	615.5	613.1	615.5	617.9	620.3
130°	665.3	665.8	666.0	664.6	661.7	658.9	656.0	653.2	656.0	658.9	661.7
132.5°	708.4	708.2	708.1	707.0	704.8	702.7	700.5	698.3	700.5	702.7	704.8
135°	748.9	748.4	748.2	747.0	744.6	742.3	739.9	737.5	739.9	742.3	744.6
137.5°	790.0	789.6	789.4	788.4	786.5	784.5	782.6	780.6	782.6	784.5	786.5
140°	829.2	828.1	827.6	826.6	824.7	822.7	820.8	818.8	820.8	822.7	824.7
142.5°	867.7	867.0	866.7	865.7	863.8	861.8	859.9	857.9	859.9	861.8	863.8
145°	904.0	902.7	902.0	901.2	899.7	898.2	896.6	895.1	896.6	898.2	899.7
147.5°	938.6	937.7	937.3	936.3	934.3	932.4	930.4	928.4	930.4	932.4	934.3
150°	969.9	969.0	968.6	967.9	966.6	965.3	964.0	962.7	964.0	965.3	966.6
152.5°	1000.6	999.5	999.0	998.3	997.0	995.7	994.4	993.1	994.4	995.7	997.0
155°	1027.4	1026.7	1026.4	1026.1	1025.4	1024.7	1024.1	1023.4	1024.1	1024.7	1025.4
157.5°	1052.5	1052.0	1051.8	1051.6	1051.2	1050.7	1050.3	1049.9	1050.3	1050.7	1051.2
160°	1075.7	1075.5	1075.4	1075.2	1074.7	1074.3	1073.8	1073.4	1073.8	1074.3	1074.7
162.5°	1095.2	1095.0	1094.9	1094.9	1094.9	1094.9	1094.9	1094.9	1094.9	1094.9	1094.9
165°	1112.6	1112.6	1112.6	1112.7	1112.9	1113.1	1113.3	1113.5	1113.3	1113.1	1112.9
167.5°	1127.3	1127.3	1127.3	1127.6	1128.3	1128.9	1129.6	1130.2	1129.6	1128.9	1128.3
170°	1139.7	1139.9	1140.0	1140.3	1141.0	1141.6	1142.3	1142.9	1142.3	1141.6	1141.0
172.5°	1148.5	1148.7	1148.8	1149.1	1149.8	1150.4	1151.1	1151.7	1151.1	1150.4	1149.8
175°	1155.0	1155.5	1155.7	1156.0	1156.7	1157.3	1158.0	1158.6	1158.0	1157.3	1156.7
177.5°	1158.9	1159.4	1159.6	1159.9	1160.6	1161.2	1161.9	1162.5	1161.9	1161.2	1160.6
180°	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6

TEST NUMBER: P1010217

CATALOG NUMBER: S122RDIP-B675D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1447.7	1448.8	1451.8	1442.7	1428.4	1422.3	1404.0	1400.9	1397.9	1397.9	1400.9
5°	1415.2	1411.1	1412.1	1394.8	1374.5	1362.3	1336.8	1340.9	1327.7	1319.5	1321.6
7.5°	1379.6	1368.4	1367.4	1345.0	1319.5	1297.2	1270.7	1264.6	1252.4	1238.2	1232.1
10°	1334.8	1326.7	1311.4	1286.0	1253.4	1235.1	1199.5	1178.1	1175.1	1153.7	1145.6
12.5°	1289.0	1274.8	1259.5	1223.9	1187.3	1157.8	1131.3	1107.9	1091.7	1073.3	1061.1
15°	1236.1	1218.8	1201.5	1163.9	1121.2	1091.7	1052.0	1017.4	969.6	931.9	910.6
17.5°	1178.1	1158.8	1135.4	1093.7	1052.0	1011.3	938.0	897.3	863.8	841.4	828.2
20°	1118.1	1096.7	1073.3	1031.6	959.4	888.2	847.5	815.9	795.6	773.2	756.9
22.5°	1055.0	1032.6	1007.2	942.1	865.8	815.9	784.4	754.9	725.4	713.2	705.0
25°	996.0	975.7	943.1	854.6	794.6	748.8	713.2	693.9	678.6	662.3	647.1
27.5°	935.0	897.3	851.6	777.3	739.6	692.8	667.4	653.2	626.7	615.5	608.4
30°	861.7	820.0	776.3	723.4	679.6	647.1	623.7	600.3	585.0	573.8	561.6
32.5°	787.5	747.8	720.3	665.4	632.8	599.2	576.9	562.6	540.2	533.1	528.0
35°	723.4	689.8	665.4	620.6	590.1	559.6	543.3	521.9	507.7	494.4	486.3
37.5°	660.3	642.0	616.5	578.9	546.3	521.9	499.5	492.4	473.1	466.0	457.8
40°	616.5	589.1	567.7	535.1	507.7	481.2	467.0	450.7	437.5	426.3	423.2
42.5°	563.6	543.3	531.1	495.5	467.0	451.7	434.4	416.1	405.9	396.8	385.6
45°	524.0	505.6	488.3	459.9	434.4	415.1	399.8	387.6	370.3	366.3	349.0
47.5°	482.2	463.9	450.7	422.2	398.8	380.5	369.3	353.0	338.8	329.6	321.5
50°	440.5	425.3	413.1	388.6	368.3	349.0	333.7	317.4	311.3	296.1	291.0
52.5°	400.8	390.7	377.4	354.0	333.7	317.4	301.1	287.9	278.8	270.6	264.5
55°	367.3	351.0	344.9	319.5	302.2	284.9	270.6	262.5	251.3	246.2	241.1
57.5°	329.6	320.5	310.3	291.0	271.6	255.4	245.2	233.0	226.9	220.8	216.7
60°	297.1	283.9	275.7	259.4	242.1	226.9	217.7	208.6	200.4	195.3	187.2
62.5°	259.4	249.3	244.2	226.9	212.6	198.4	190.3	181.1	175.0	165.8	155.7
65°	226.9	218.7	212.6	198.4	185.2	171.9	163.8	152.6	144.5	139.4	138.4
67.5°	198.4	192.3	183.1	169.9	156.7	146.5	137.3	128.2	127.2	125.1	125.1
70°	166.9	160.7	155.7	141.4	130.2	119.0	117.0	113.9	110.9	109.9	107.8
72.5°	139.4	134.3	128.2	116.0	104.8	101.7	99.7	97.7	94.6	93.6	92.6
75°	112.9	105.8	101.7	90.5	87.5	85.5	83.4	80.4	78.3	77.3	75.3
77.5°	86.5	79.4	79.4	73.3	71.2	68.2	66.1	64.1	63.1	61.0	61.0
80°	61.0	61.0	59.0	56.0	52.9	51.9	48.8	47.8	46.8	47.8	45.8
82.5°	44.8	40.7	40.7	38.7	36.6	35.6	33.6	33.6	32.6	32.6	32.6
85°	25.4	25.4	24.4	22.4	21.4	21.4	20.3	20.3	19.3	19.3	18.3
87.5°	10.2	9.2	10.2	9.2	9.2	8.1	8.1	8.1	7.1	8.1	7.1
90°	11.4	12.7	15.1	19.9	24.7	29.5	34.3	33.9	33.4	33.0	32.5
92.5°	28.5	29.4	29.5	29.7	30.0	30.2	30.4	30.6	30.8	31.0	31.2
95°	59.6	60.7	60.9	61.4	61.8	62.3	62.7	62.7	62.7	62.7	62.7
97.5°	93.0	94.0	94.4	95.3	96.2	97.0	97.9	97.9	97.9	97.9	97.9
100°	131.3	132.2	132.5	133.2	133.9	134.5	135.2	135.2	135.2	135.2	135.2
102.5°	170.7	171.4	171.8	172.7	173.6	174.4	175.3	175.5	175.7	176.0	176.2
105°	213.2	213.5	213.7	214.2	214.6	215.1	215.5	215.9	216.3	216.8	217.2
107.5°	259.1	259.5	259.5	259.5	259.5	259.5	259.5	259.7	259.9	260.2	260.4
110°	303.9	304.6	304.6	304.6	304.6	304.6	304.6	304.6	304.6	304.6	304.6

TEST NUMBER: P1010217

CATALOG NUMBER: S122RDIP-B675D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	350.9	351.6	351.5	351.3	351.0	350.8	350.6	350.0	349.3	348.7	348.0
115°	396.9	397.6	397.4	397.0	396.5	396.1	395.7	395.5	395.3	395.0	394.8
117.5°	444.7	445.6	445.1	444.0	442.9	441.8	440.7	440.1	439.4	438.8	438.1
120°	490.7	491.6	490.7	489.0	487.3	485.5	483.8	483.8	483.8	483.8	483.8
122.5°	534.6	535.7	535.2	534.1	533.0	531.9	530.8	530.2	529.5	528.9	528.2
125°	577.8	578.8	578.5	577.8	577.2	576.5	575.9	575.2	574.6	573.9	573.2
127.5°	622.7	623.9	623.5	622.6	621.7	620.8	619.9	619.0	618.2	617.3	616.4
130°	664.6	666.0	665.8	665.3	664.9	664.4	664.0	663.6	663.2	662.7	662.3
132.5°	707.0	708.1	708.2	708.4	708.7	708.9	709.1	708.0	706.9	705.8	704.7
135°	747.0	748.2	748.4	748.9	749.3	749.8	750.2	750.0	749.8	749.5	749.3
137.5°	788.4	789.4	789.6	790.0	790.5	790.9	791.3	791.1	790.9	790.7	790.5
140°	826.6	827.6	828.1	829.2	830.3	831.4	832.5	832.5	832.5	832.5	832.5
142.5°	865.7	866.7	867.0	867.7	868.4	869.0	869.7	869.9	870.1	870.4	870.6
145°	901.2	902.0	902.7	904.0	905.3	906.6	907.9	908.1	908.3	908.6	908.8
147.5°	936.3	937.3	937.7	938.6	939.5	940.3	941.2	941.6	942.0	942.5	942.9
150°	967.9	968.6	969.0	969.9	970.8	971.6	972.5	973.2	973.8	974.5	975.2
152.5°	998.3	999.0	999.5	1000.6	1001.7	1002.8	1003.9	1004.8	1005.6	1006.5	1007.4
155°	1026.1	1026.4	1026.7	1027.4	1028.0	1028.7	1029.3	1030.4	1031.5	1032.6	1033.7
157.5°	1051.6	1051.8	1052.0	1052.5	1052.9	1053.4	1053.8	1055.3	1056.9	1058.4	1059.9
160°	1075.2	1075.4	1075.5	1075.7	1075.9	1076.1	1076.3	1077.6	1078.9	1080.2	1081.5
162.5°	1094.9	1094.9	1095.0	1095.2	1095.5	1095.7	1095.9	1097.4	1099.0	1100.5	1102.0
165°	1112.7	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1114.1	1115.6	1117.1	1118.6
167.5°	1127.6	1127.3	1127.3	1127.3	1127.3	1127.3	1127.3	1128.8	1130.3	1131.8	1133.3
170°	1140.3	1140.0	1139.9	1139.7	1139.4	1139.2	1139.0	1140.5	1142.1	1143.6	1145.1
172.5°	1149.1	1148.8	1148.7	1148.5	1148.2	1148.0	1147.8	1149.3	1150.9	1152.4	1153.9
175°	1156.0	1155.7	1155.5	1155.0	1154.6	1154.1	1153.7	1155.2	1156.8	1158.3	1159.8
177.5°	1159.9	1159.6	1159.4	1158.9	1158.5	1158.0	1157.6	1158.9	1160.2	1161.5	1162.8
180°	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6

TEST NUMBER: P1010217

CATALOG NUMBER: S122RDIP-B675D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1400.9	1398.9	1392.8	1394.8	1391.8	1391.8	1389.7	1389.7	1389.7	1394.8	1391.8
5°	1324.6	1317.5	1310.4	1307.3	1304.3	1301.2	1301.2	1300.2	1309.4	1307.3	1315.5
7.5°	1230.0	1228.0	1213.7	1213.7	1208.7	1206.6	1211.7	1212.7	1213.7	1215.8	1220.9
10°	1145.6	1140.5	1120.1	1122.2	1119.1	1115.1	1118.1	1116.1	1123.2	1125.2	1123.2
12.5°	1045.9	1036.7	1014.3	1003.1	990.9	981.8	993.0	984.8	1013.3	1021.5	1043.8
15°	913.6	896.3	881.1	881.1	869.9	861.7	866.8	876.0	882.1	891.2	895.3
17.5°	825.1	818.0	805.8	798.6	795.6	792.5	792.5	796.6	809.8	808.8	817.0
20°	749.8	745.7	739.6	730.5	727.4	725.4	725.4	725.4	734.6	742.7	747.8
22.5°	697.9	694.9	690.8	678.6	672.5	670.5	675.5	678.6	685.7	691.8	696.9
25°	646.0	638.9	631.8	627.7	624.7	624.7	626.7	627.7	630.8	633.8	639.9
27.5°	603.3	598.2	588.0	576.9	576.9	573.8	575.8	577.9	585.0	595.2	600.3
30°	555.5	554.5	550.4	546.3	542.3	540.2	544.3	547.4	548.4	553.5	553.5
32.5°	520.9	513.8	506.7	502.6	500.6	499.5	500.6	504.6	504.6	510.7	517.8
35°	486.3	482.2	475.1	468.0	466.0	460.9	464.9	469.0	476.1	479.2	482.2
37.5°	448.7	443.6	440.5	438.5	434.4	435.4	432.4	438.5	444.6	443.6	445.6
40°	420.2	411.0	401.9	400.8	399.8	398.8	398.8	399.8	403.9	408.0	414.1
42.5°	383.6	380.5	372.4	364.2	362.2	360.2	358.1	362.2	370.3	377.4	380.5
45°	345.9	341.8	339.8	333.7	329.6	328.6	326.6	331.7	338.8	341.8	343.9
47.5°	311.3	310.3	304.2	305.2	302.2	303.2	302.2	305.2	305.2	308.3	310.3
50°	287.9	284.9	281.8	279.8	276.7	276.7	275.7	276.7	280.8	284.9	283.9
52.5°	264.5	259.4	258.4	257.4	255.4	257.4	254.3	255.4	259.4	261.5	260.5
55°	237.1	236.0	234.0	232.0	230.9	229.9	229.9	229.9	234.0	237.1	238.1
57.5°	215.7	210.6	206.5	206.5	202.5	201.4	203.5	204.5	207.5	209.6	211.6
60°	186.2	184.1	178.0	175.0	168.9	167.9	167.9	171.9	177.0	184.1	186.2
62.5°	154.6	151.6	150.6	150.6	150.6	150.6	150.6	150.6	150.6	151.6	151.6
65°	137.3	138.4	137.3	136.3	137.3	137.3	136.3	136.3	136.3	137.3	138.4
67.5°	123.1	122.1	123.1	122.1	121.1	121.1	120.1	121.1	122.1	123.1	123.1
70°	106.8	106.8	105.8	106.8	105.8	104.8	103.8	103.8	105.8	106.8	106.8
72.5°	91.6	91.6	90.5	90.5	88.5	88.5	89.5	88.5	88.5	91.6	91.6
75°	76.3	75.3	74.3	74.3	73.3	73.3	73.3	72.2	74.3	74.3	75.3
77.5°	60.0	60.0	60.0	59.0	59.0	58.0	58.0	59.0	59.0	59.0	60.0
80°	45.8	45.8	45.8	44.8	43.7	43.7	43.7	43.7	43.7	44.8	43.7
82.5°	31.5	31.5	31.5	31.5	31.5	30.5	30.5	30.5	31.5	31.5	30.5
85°	19.3	18.3	19.3	19.3	18.3	19.3	18.3	18.3	17.3	17.3	18.3
87.5°	8.1	7.1	6.1	6.1	7.1	6.1	6.1	6.1	7.1	6.1	6.1
90°	32.3	32.4	32.6	32.9	33.1	33.3	33.1	32.9	32.6	32.4	32.3
92.5°	31.3	31.3	31.3	31.3	31.3	31.3	31.3	31.3	31.3	31.3	31.3
95°	62.7	62.5	62.0	61.6	61.1	60.7	61.1	61.6	62.0	62.5	62.7
97.5°	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9
100°	135.2	135.1	134.9	134.6	134.4	134.2	134.4	134.6	134.9	135.1	135.2
102.5°	176.3	176.2	176.0	175.7	175.5	175.3	175.5	175.7	176.0	176.2	176.3
105°	217.4	217.4	217.4	217.4	217.4	217.4	217.4	217.4	217.4	217.4	217.4
107.5°	260.5	260.0	258.9	257.8	256.7	255.6	256.7	257.8	258.9	260.0	260.5
110°	304.6	304.3	303.6	302.9	302.3	301.6	302.3	302.9	303.6	304.3	304.6

TEST NUMBER: P1010217

CATALOG NUMBER: S122RDIP-B675D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	347.7	347.5	347.0	346.6	346.1	345.7	346.1	346.6	347.0	347.5	347.7
115°	394.7	394.4	393.7	393.0	392.4	391.7	392.4	393.0	393.7	394.4	394.7
117.5°	437.8	437.5	436.8	436.1	435.5	434.8	435.5	436.1	436.8	437.5	437.8
120°	483.8	483.5	482.8	482.2	481.5	480.9	481.5	482.2	482.8	483.5	483.8
122.5°	527.9	527.7	527.2	526.8	526.3	525.9	526.3	526.8	527.2	527.7	527.9
125°	572.9	572.8	572.6	572.4	572.2	572.0	572.2	572.4	572.6	572.8	572.9
127.5°	616.0	615.7	615.0	614.4	613.7	613.1	613.7	614.4	615.0	615.7	616.0
130°	662.1	661.7	660.8	659.9	659.0	658.1	659.0	659.9	660.8	661.7	662.1
132.5°	704.2	703.9	703.2	702.5	701.9	701.2	701.9	702.5	703.2	703.9	704.2
135°	749.2	748.9	748.2	747.6	746.9	746.3	746.9	747.6	748.2	748.9	749.2
137.5°	790.4	790.0	789.1	788.2	787.3	786.4	787.3	788.2	789.1	790.0	790.4
140°	832.5	832.1	831.2	830.3	829.4	828.5	829.4	830.3	831.2	832.1	832.5
142.5°	870.7	870.3	869.4	868.5	867.6	866.7	867.6	868.5	869.4	870.3	870.7
145°	908.9	908.5	907.6	906.7	905.8	904.9	905.8	906.7	907.6	908.5	908.9
147.5°	943.1	942.7	941.8	940.9	940.1	939.2	940.1	940.9	941.8	942.7	943.1
150°	975.5	975.2	974.5	973.8	973.2	972.5	973.2	973.8	974.5	975.2	975.5
152.5°	1007.8	1007.4	1006.5	1005.6	1004.8	1003.9	1004.8	1005.6	1006.5	1007.4	1007.8
155°	1034.2	1033.9	1033.2	1032.6	1031.9	1031.3	1031.9	1032.6	1033.2	1033.9	1034.2
157.5°	1060.7	1060.2	1059.1	1058.0	1056.9	1055.8	1056.9	1058.0	1059.1	1060.2	1060.7
160°	1082.2	1081.8	1080.9	1080.0	1079.2	1078.3	1079.2	1080.0	1080.9	1081.8	1082.2
162.5°	1102.8	1102.3	1101.2	1100.1	1099.0	1097.9	1099.0	1100.1	1101.2	1102.3	1102.8
165°	1119.4	1118.9	1117.8	1116.7	1115.6	1114.5	1115.6	1116.7	1117.8	1118.9	1119.4
167.5°	1134.1	1133.6	1132.5	1131.4	1130.3	1129.2	1130.3	1131.4	1132.5	1133.6	1134.1
170°	1145.9	1145.2	1143.9	1142.6	1141.3	1140.0	1141.3	1142.6	1143.9	1145.2	1145.9
172.5°	1154.7	1154.0	1152.7	1151.4	1150.1	1148.8	1150.1	1151.4	1152.7	1154.0	1154.7
175°	1160.6	1159.9	1158.6	1157.3	1156.0	1154.7	1156.0	1157.3	1158.6	1159.9	1160.6
177.5°	1163.5	1162.8	1161.5	1160.2	1158.9	1157.6	1158.9	1160.2	1161.5	1162.8	1163.5
180°	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6

TEST NUMBER: P1010217

CATALOG NUMBER: S122RDIP-B675D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1394.8	1399.9	1397.9	1386.7	1397.9	1400.9	1407.0	1413.1	1417.2	1423.3	1428.4
5°	1307.3	1317.5	1323.6	1317.5	1337.9	1340.9	1355.2	1363.3	1375.5	1385.7	1393.8
7.5°	1224.9	1233.1	1245.3	1247.3	1259.5	1273.8	1294.1	1314.5	1333.8	1344.0	1353.1
10°	1136.4	1150.7	1169.0	1164.9	1183.2	1205.6	1227.0	1259.5	1275.8	1294.1	1310.4
12.5°	1047.9	1057.1	1081.5	1089.6	1116.1	1133.4	1162.9	1183.2	1223.9	1245.3	1259.5
15°	893.3	930.9	961.4	998.1	1032.6	1065.2	1091.7	1128.3	1163.9	1180.2	1203.6
17.5°	823.1	840.4	858.7	877.0	921.7	979.7	1026.5	1066.2	1096.7	1118.1	1145.6
20°	749.8	767.1	787.5	804.8	832.2	873.9	931.9	1000.1	1036.7	1059.1	1085.5
22.5°	697.9	714.2	727.4	742.7	764.1	794.6	838.3	922.8	971.6	999.1	1022.5
25°	642.0	662.3	676.6	687.8	705.0	738.6	774.2	822.0	909.5	930.9	963.5
27.5°	603.3	609.4	625.7	643.0	660.3	678.6	715.2	755.9	814.9	861.7	901.4
30°	557.5	572.8	588.0	595.2	610.4	636.9	659.3	703.0	748.8	785.4	833.2
32.5°	522.9	532.1	542.3	559.6	573.8	592.1	614.5	651.1	689.8	713.2	749.8
35°	484.3	490.4	511.7	518.9	533.1	551.4	573.8	602.3	644.0	662.3	688.8
37.5°	447.6	461.9	468.0	484.3	497.5	515.8	532.1	564.6	592.1	613.5	637.9
40°	419.2	425.3	436.5	450.7	461.9	476.1	496.5	519.9	549.4	566.7	588.0
42.5°	384.6	389.7	403.9	412.0	430.4	443.6	455.8	484.3	510.7	524.0	545.3
45°	346.9	359.1	368.3	384.6	394.7	411.0	426.3	446.6	471.0	486.3	498.5
47.5°	314.4	326.6	335.7	351.0	367.3	374.4	390.7	412.0	434.4	446.6	463.9
50°	287.9	292.0	309.3	316.4	333.7	347.9	359.1	377.4	401.9	409.0	423.2
52.5°	262.5	265.5	276.7	285.9	301.1	313.4	327.6	344.9	365.2	376.4	387.6
55°	240.1	242.1	247.2	257.4	267.6	282.8	296.1	312.3	329.6	341.8	352.0
57.5°	214.7	218.7	222.8	228.9	239.1	253.3	267.6	282.8	297.1	305.2	318.4
60°	185.2	191.3	198.4	205.5	212.6	222.8	239.1	253.3	266.6	273.7	283.9
62.5°	153.6	165.8	171.9	180.1	186.2	195.3	207.5	223.8	233.0	242.1	250.3
65°	138.4	139.4	140.4	148.5	159.7	168.9	180.1	192.3	206.5	212.6	218.7
67.5°	123.1	124.1	126.2	127.2	131.2	141.4	153.6	166.9	178.0	182.1	188.2
70°	107.8	107.8	111.9	112.9	113.9	115.0	125.1	138.4	148.5	153.6	160.7
72.5°	91.6	92.6	94.6	95.6	97.7	99.7	102.8	109.9	122.1	127.2	135.3
75°	75.3	76.3	77.3	78.3	81.4	82.4	85.5	89.5	94.6	100.7	105.8
77.5°	60.0	60.0	61.0	63.1	65.1	66.1	69.2	71.2	73.3	76.3	80.4
80°	44.8	45.8	45.8	47.8	47.8	48.8	49.9	52.9	54.9	57.0	59.0
82.5°	30.5	32.6	32.6	32.6	33.6	34.6	35.6	35.6	37.6	38.7	41.7
85°	18.3	19.3	19.3	19.3	18.3	20.3	20.3	21.4	21.4	21.4	22.4
87.5°	7.1	6.1	7.1	7.1	7.1	8.1	7.1	7.1	8.1	9.2	9.2
90°	32.5	33.0	33.4	33.9	34.3	29.5	24.7	19.9	15.1	12.7	11.4
92.5°	31.2	31.0	30.8	30.6	30.4	30.2	30.0	29.7	29.5	29.4	28.5
95°	62.7	62.7	62.7	62.7	62.7	62.3	61.8	61.4	60.9	60.7	59.6
97.5°	97.9	97.9	97.9	97.9	97.9	97.0	96.2	95.3	94.4	94.0	93.0
100°	135.2	135.2	135.2	135.2	135.2	134.5	133.9	133.2	132.5	132.2	131.3
102.5°	176.2	176.0	175.7	175.5	175.3	174.4	173.6	172.7	171.8	171.4	170.7
105°	217.2	216.8	216.3	215.9	215.5	215.1	214.6	214.2	213.7	213.5	213.2
107.5°	260.4	260.2	259.9	259.7	259.5	259.5	259.5	259.5	259.5	259.5	259.1
110°	304.6	304.6	304.6	304.6	304.6	304.6	304.6	304.6	304.6	304.6	303.9

TEST NUMBER: P1010217

CATALOG NUMBER: S122RDIP-B675D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	348.0	348.7	349.3	350.0	350.6	350.8	351.0	351.3	351.5	351.6	350.9
115°	394.8	395.0	395.3	395.5	395.7	396.1	396.5	397.0	397.4	397.6	396.9
117.5°	438.1	438.8	439.4	440.1	440.7	441.8	442.9	444.0	445.1	445.6	444.7
120°	483.8	483.8	483.8	483.8	483.8	485.5	487.3	489.0	490.7	491.6	490.7
122.5°	528.2	528.9	529.5	530.2	530.8	531.9	533.0	534.1	535.2	535.7	534.6
125°	573.2	573.9	574.6	575.2	575.9	576.5	577.2	577.8	578.5	578.8	577.8
127.5°	616.4	617.3	618.2	619.0	619.9	620.8	621.7	622.6	623.5	623.9	622.7
130°	662.3	662.7	663.2	663.6	664.0	664.4	664.9	665.3	665.8	666.0	664.6
132.5°	704.7	705.8	706.9	708.0	709.1	708.9	708.7	708.4	708.2	708.1	707.0
135°	749.3	749.5	749.8	750.0	750.2	749.8	749.3	748.9	748.4	748.2	747.0
137.5°	790.5	790.7	790.9	791.1	791.3	790.9	790.5	790.0	789.6	789.4	788.4
140°	832.5	832.5	832.5	832.5	832.5	831.4	830.3	829.2	828.1	827.6	826.6
142.5°	870.6	870.4	870.1	869.9	869.7	869.0	868.4	867.7	867.0	866.7	865.7
145°	908.8	908.6	908.3	908.1	907.9	906.6	905.3	904.0	902.7	902.0	901.2
147.5°	942.9	942.5	942.0	941.6	941.2	940.3	939.5	938.6	937.7	937.3	936.3
150°	975.2	974.5	973.8	973.2	972.5	971.6	970.8	969.9	969.0	968.6	967.9
152.5°	1007.4	1006.5	1005.6	1004.8	1003.9	1002.8	1001.7	1000.6	999.5	999.0	998.3
155°	1033.7	1032.6	1031.5	1030.4	1029.3	1028.7	1028.0	1027.4	1026.7	1026.4	1026.1
157.5°	1059.9	1058.4	1056.9	1055.3	1053.8	1053.4	1052.9	1052.5	1052.0	1051.8	1051.6
160°	1081.5	1080.2	1078.9	1077.6	1076.3	1076.1	1075.9	1075.7	1075.5	1075.4	1075.2
162.5°	1102.0	1100.5	1099.0	1097.4	1095.9	1095.7	1095.5	1095.2	1095.0	1094.9	1094.9
165°	1118.6	1117.1	1115.6	1114.1	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.7
167.5°	1133.3	1131.8	1130.3	1128.8	1127.3	1127.3	1127.3	1127.3	1127.3	1127.3	1127.6
170°	1145.1	1143.6	1142.1	1140.5	1139.0	1139.2	1139.4	1139.7	1139.9	1140.0	1140.3
172.5°	1153.9	1152.4	1150.9	1149.3	1147.8	1148.0	1148.2	1148.5	1148.7	1148.8	1149.1
175°	1159.8	1158.3	1156.8	1155.2	1153.7	1154.1	1154.6	1155.0	1155.5	1155.7	1156.0
177.5°	1162.8	1161.5	1160.2	1158.9	1157.6	1158.0	1158.5	1158.9	1159.4	1159.6	1159.9
180°	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6

TEST NUMBER: P1010217

CATALOG NUMBER: S122RDIP-B675D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1464.0	1464.0	1464.0	1464.0
2.5°	1437.6	1434.5	1452.8	1473.2
5°	1408.1	1413.1	1436.5	1465.0
7.5°	1377.5	1388.7	1416.2	1453.8
10°	1334.8	1355.2	1396.9	1435.5
12.5°	1293.1	1320.6	1360.2	1406.0
15°	1246.3	1276.8	1325.7	1380.6
17.5°	1194.4	1229.0	1286.0	1346.0
20°	1139.5	1185.3	1245.3	1310.4
22.5°	1078.4	1133.4	1195.4	1267.7
25°	1019.4	1079.4	1141.5	1224.9
27.5°	961.4	1020.4	1089.6	1174.1
30°	903.4	957.4	1031.6	1122.2
32.5°	841.4	897.3	975.7	1068.3
35°	784.4	840.4	913.6	1005.2
37.5°	723.4	783.4	853.6	948.2
40°	652.1	722.3	790.5	881.1
42.5°	593.1	667.4	733.5	819.0
45°	546.3	616.5	671.5	754.9
47.5°	502.6	559.6	615.5	692.8
50°	460.9	504.6	562.6	631.8
52.5°	418.1	455.8	505.6	570.8
55°	379.5	415.1	459.9	509.7
57.5°	343.9	369.3	414.1	458.8
60°	304.2	330.6	365.2	402.9
62.5°	270.6	291.0	323.5	355.1
65°	235.0	254.3	278.8	308.3
67.5°	202.5	219.8	239.1	262.5
70°	173.0	186.2	200.4	220.8
72.5°	141.4	155.7	168.9	185.2
75°	116.0	122.1	133.3	144.5
77.5°	89.5	97.7	103.8	112.9
80°	64.1	71.2	73.3	80.4
82.5°	42.7	46.8	50.9	52.9
85°	24.4	26.5	30.5	31.5
87.5°	9.2	10.2	12.2	14.2
90°	8.8	6.2	3.6	1.0
92.5°	26.8	25.0	23.3	21.5
95°	57.4	55.3	53.1	50.9
97.5°	91.1	89.1	87.2	85.2
100°	129.6	127.9	126.1	124.4
102.5°	169.4	168.1	166.8	165.5
105°	212.5	211.9	211.2	210.6
107.5°	258.2	257.3	256.5	255.6
110°	302.6	301.3	300.0	298.7

TEST NUMBER: P1010217

CATALOG NUMBER: S122RDIP-B675D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	349.6	348.3	347.0	345.7
115°	395.6	394.3	393.0	391.7
117.5°	443.0	441.3	439.5	437.8
120°	489.0	487.3	485.5	483.8
122.5°	532.4	530.3	528.1	525.9
125°	575.9	573.9	572.0	570.0
127.5°	620.3	617.9	615.5	613.1
130°	661.7	658.9	656.0	653.2
132.5°	704.8	702.7	700.5	698.3
135°	744.6	742.3	739.9	737.5
137.5°	786.5	784.5	782.6	780.6
140°	824.7	822.7	820.8	818.8
142.5°	863.8	861.8	859.9	857.9
145°	899.7	898.2	896.6	895.1
147.5°	934.3	932.4	930.4	928.4
150°	966.6	965.3	964.0	962.7
152.5°	997.0	995.7	994.4	993.1
155°	1025.4	1024.7	1024.1	1023.4
157.5°	1051.2	1050.7	1050.3	1049.9
160°	1074.7	1074.3	1073.8	1073.4
162.5°	1094.9	1094.9	1094.9	1094.9
165°	1112.9	1113.1	1113.3	1113.5
167.5°	1128.3	1128.9	1129.6	1130.2
170°	1141.0	1141.6	1142.3	1142.9
172.5°	1149.8	1150.4	1151.1	1151.7
175°	1156.7	1157.3	1158.0	1158.6
177.5°	1160.6	1161.2	1161.9	1162.5
180°	1160.6	1160.6	1160.6	1160.6

(END OF REPORT)