

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010229

Luminaire Tested: S122RDIP-B675D925UB35-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010229
REPORT IS A COMBINATION OF REPORTS P988601 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B675D925UB35-4F0-XX-W2A-A1
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5854.0 lumens
Efficiency: N/A
Efficacy: 90.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010229

CATALOG NUMBER: S122RDIP-B675D925UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1010229

CATALOG NUMBER: S122RDIP-B675D925UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50
1	97	93	89	86	89	85	82	80	71	69	67	58	56	55	46	45	44
2	89	82	76	72	81	75	71	66	63	60	57	52	49	47	41	39	38
3	82	73	66	60	75	67	61	56	56	52	48	46	43	41	37	35	33
4	75	65	58	52	69	60	53	48	51	46	42	42	38	36	34	31	29
5	69	58	51	45	63	54	47	42	46	41	37	38	34	31	31	28	26
6	64	53	45	39	59	49	42	37	41	36	32	35	31	28	28	26	23
7	59	48	40	35	54	44	38	33	38	33	29	32	28	25	26	23	21
8	55	44	36	31	51	40	34	29	35	30	26	29	25	23	24	21	19
9	52	40	33	28	47	37	31	26	32	27	23	27	23	21	22	20	18
10	48	37	30	25	44	34	28	24	30	25	21	25	21	19	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23476	23476	23476	23476
5°	23531	24936	23613	19921
10°	23273	26356	23438	16450
15°	22767	26365	23153	12359
20°	22160	21793	22641	10196
25°	21423	13618	21886	8673
30°	20483	8719	21040	7468
35°	19339	6701	19966	6390
40°	18063	5632	18837	5589
45°	16701	4794	17400	4692
50°	15305	4074	16020	4058
55°	13760	3540	14501	3493
60°	12384	2699	13042	2667
65°	11102	2031	11760	2304
70°	9688	1622	10446	1879
75°	8190	1242	8939	1420
80°	6499	845	6994	931
85°	4520	437	4944	461

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 21476 cd/sqm

TEST NUMBER: P1010229

CATALOG NUMBER: S122RDIP-B675D925UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.7	2.4
10°-20°	392.7	6.7
20°-30°	505.4	8.6
30°-40°	479.4	8.2
40°-50°	410.9	7.0
50°-60°	312.9	5.3
60°-70°	197.3	3.4
70°-80°	98.4	1.7
80°-90°	28.7	0.5
90°-100°	72.7	1.2
100°-110°	231.3	4.0
110°-120°	395.7	6.8
120°-130°	520.4	8.9
130°-140°	584.1	10.0
140°-150°	572.8	9.8
150°-160°	480.5	8.2
160°-170°	318.7	5.4
170°-180°	111.4	1.9
0°-30°	1038.7	17.7
0°-40°	1518.1	25.9
0°-60°	2241.9	38.3
0°-90°	2566.3	43.8
90°-120°	699.7	12.0
90°-150°	2377.1	40.6
90°-180°	3288.0	56.2
0°-180°	5854.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1483	1483	1483	1483	1483	
5°	1484	1650	1489	1318	1484	141
15°	1399	1862	1422	873	1399	393
25°	1241	994	1268	633	1241	570
35°	1018	490	1051	467	1018	637
45°	765	340	797	333	765	590
55°	516	236	544	233	516	465
65°	312	123	331	139	312	310
75°	146	65	160	74	146	158
85°	32	19	35	20	32	36
90°	1	34	1	34	1	5
95°	52	62	52	62	52	58
105°	213	220	213	220	213	225
115°	397	397	397	397	397	393
125°	578	580	578	580	578	516
135°	747	756	747	756	747	577
145°	907	917	907	917	907	567
155°	1037	1045	1037	1045	1037	477
165°	1128	1129	1128	1129	1128	318
175°	1174	1170	1174	1170	1174	112
180°	1176	1176	1176	1176	1176	

TEST NUMBER: P1010229

CATALOG NUMBER: S122RDIP-B675D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1492.4	1498.6	1501.7	1505.8	1515.1	1521.2	1530.5	1532.6	1531.6	1535.7	1524.3
5°	1484.1	1497.5	1509.9	1520.2	1536.7	1547.0	1558.3	1571.7	1574.8	1590.3	1581.0
7.5°	1472.8	1492.4	1509.9	1530.5	1555.3	1568.7	1586.2	1606.8	1616.1	1634.6	1639.8
10°	1454.3	1482.1	1512.0	1533.6	1567.6	1591.3	1607.8	1640.8	1662.4	1690.3	1686.1
12.5°	1424.4	1460.4	1500.6	1536.7	1581.0	1596.5	1627.4	1661.4	1689.2	1715.0	1737.7
15°	1398.6	1439.8	1484.1	1528.5	1579.0	1607.8	1638.7	1683.1	1712.9	1758.3	1777.9
17.5°	1363.6	1416.1	1468.7	1518.2	1577.9	1610.9	1649.0	1692.3	1736.7	1779.9	1795.4
20°	1327.5	1384.2	1440.9	1507.8	1575.9	1607.8	1647.0	1700.6	1743.9	1777.9	1777.9
22.5°	1284.2	1353.2	1418.2	1482.1	1556.3	1602.7	1642.9	1705.7	1736.7	1743.9	1716.0
25°	1240.9	1310.0	1381.1	1460.4	1545.0	1586.2	1631.5	1690.3	1700.6	1671.7	1599.6
27.5°	1189.4	1266.7	1347.1	1432.6	1521.2	1572.8	1614.0	1653.2	1633.6	1556.3	1443.9
30°	1136.8	1220.3	1311.0	1392.4	1499.6	1547.0	1582.1	1593.4	1531.6	1405.8	1260.5
32.5°	1082.2	1163.6	1259.5	1357.4	1465.6	1510.9	1533.6	1503.7	1390.4	1231.6	1054.4
35°	1018.3	1110.0	1210.0	1312.0	1419.2	1453.2	1466.6	1393.4	1248.1	1043.0	866.8
37.5°	960.6	1052.3	1159.5	1263.6	1367.7	1386.2	1372.8	1258.4	1073.9	870.9	698.8
40°	892.5	990.5	1095.6	1212.0	1297.6	1302.7	1269.8	1121.4	892.5	701.9	595.7
42.5°	829.7	928.6	1033.7	1152.3	1217.2	1199.7	1155.4	960.6	745.2	605.0	519.4
45°	764.7	858.5	971.9	1077.0	1123.4	1082.2	1015.2	808.0	625.6	520.5	454.5
47.5°	701.9	789.5	901.8	1002.8	1011.1	964.7	885.3	677.1	542.1	457.6	404.0
50°	640.0	727.6	832.8	916.3	908.0	844.1	754.4	588.5	471.0	404.0	359.7
52.5°	578.2	657.6	759.6	825.6	790.5	728.7	640.0	498.8	411.2	352.5	318.5
55°	516.4	590.6	678.2	732.8	677.1	606.0	543.2	427.7	356.6	309.2	283.4
57.5°	464.8	523.6	604.0	636.9	570.0	514.3	459.7	367.9	309.2	275.2	245.3
60°	408.1	461.7	527.7	547.3	478.2	432.9	386.5	311.3	264.9	235.0	215.4
62.5°	359.7	404.0	454.5	454.5	393.7	359.7	324.7	260.8	222.6	198.9	189.6
65°	312.3	344.2	380.3	376.2	324.7	294.8	266.9	215.4	186.5	170.1	160.8
67.5°	265.9	290.6	314.3	299.9	262.8	237.1	211.3	174.2	154.6	143.3	130.9
70°	223.7	243.2	255.6	242.2	205.1	183.5	164.9	140.2	124.7	110.3	103.1
72.5°	187.6	195.8	199.9	183.5	152.5	140.2	126.8	109.2	95.9	88.6	86.6
75°	146.4	153.6	150.5	138.1	112.3	103.1	92.8	80.4	77.3	73.2	71.1
77.5°	114.4	114.4	109.2	97.9	80.4	73.2	69.1	62.9	59.8	58.7	56.7
80°	81.4	80.4	77.3	64.9	54.6	50.5	50.5	46.4	45.3	43.3	43.3
82.5°	53.6	53.6	49.5	39.2	36.1	35.0	34.0	32.0	32.0	30.9	30.9
85°	32.0	29.9	24.7	21.6	20.6	20.6	19.6	18.6	19.6	18.6	18.6
87.5°	14.4	11.3	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2
90°	1.0	3.6	6.3	8.9	11.6	12.9	15.3	20.2	25.0	29.9	34.7
92.5°	21.8	23.6	25.4	27.1	28.9	29.8	29.9	30.1	30.4	30.6	30.8
95°	51.6	53.8	56.0	58.2	60.4	61.5	61.7	62.2	62.6	63.1	63.5
97.5°	86.3	88.3	90.3	92.3	94.3	95.3	95.7	96.6	97.5	98.3	99.2
100°	126.0	127.8	129.6	131.3	133.1	134.0	134.3	135.0	135.6	136.3	136.9
102.5°	167.7	169.0	170.4	171.7	173.0	173.7	174.1	175.0	175.9	176.7	177.6
105°	213.4	214.0	214.7	215.3	216.0	216.3	216.5	217.0	217.4	217.9	218.3
107.5°	259.0	259.9	260.8	261.7	262.6	263.0	263.0	263.0	263.0	263.0	263.0
110°	302.7	304.0	305.3	306.6	307.9	308.6	308.6	308.6	308.6	308.6	308.6

TEST NUMBER: P1010229

CATALOG NUMBER: S122RDIP-B675D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	350.3	351.6	352.9	354.2	355.5	356.2	356.1	355.9	355.7	355.5	355.3
115°	396.9	398.2	399.6	400.9	402.2	402.9	402.7	402.2	401.8	401.3	400.9
117.5°	443.6	445.4	447.1	448.9	450.6	451.5	451.0	449.9	448.8	447.7	446.6
120°	490.2	492.0	493.8	495.5	497.3	498.2	497.3	495.5	493.8	492.0	490.2
122.5°	532.9	535.1	537.3	539.5	541.7	542.8	542.2	541.1	540.0	538.9	537.8
125°	577.5	579.5	581.5	583.5	585.5	586.5	586.2	585.5	584.8	584.2	583.5
127.5°	621.2	623.6	626.0	628.5	630.9	632.1	631.7	630.8	629.9	629.1	628.2
130°	661.9	664.8	667.6	670.5	673.4	674.8	674.6	674.1	673.7	673.2	672.8
132.5°	707.5	709.7	711.9	714.2	716.4	717.5	717.6	717.8	718.1	718.3	718.5
135°	747.2	749.6	752.0	754.5	756.9	758.1	758.3	758.8	759.2	759.7	760.1
137.5°	790.9	792.9	794.9	796.8	798.8	799.8	800.0	800.5	800.9	801.4	801.8
140°	829.6	831.6	833.6	835.5	837.5	838.5	839.1	840.2	841.3	842.4	843.5
142.5°	869.3	871.3	873.3	875.2	877.2	878.2	878.5	879.2	879.9	880.5	881.2
145°	907.0	908.5	910.1	911.6	913.1	913.9	914.6	915.9	917.2	918.6	919.9
147.5°	940.7	942.7	944.7	946.7	948.7	949.7	950.1	951.0	951.9	952.7	953.6
150°	975.5	976.8	978.1	979.4	980.7	981.4	981.8	982.7	983.6	984.5	985.4
152.5°	1006.2	1007.5	1008.9	1010.2	1011.5	1012.2	1012.7	1013.8	1014.9	1016.0	1017.1
155°	1037.0	1037.7	1038.3	1039.0	1039.7	1040.0	1040.3	1041.0	1041.6	1042.3	1042.9
157.5°	1063.8	1064.2	1064.7	1065.1	1065.6	1065.8	1066.0	1066.5	1066.9	1067.4	1067.8
160°	1087.6	1088.0	1088.5	1088.9	1089.4	1089.6	1089.7	1089.9	1090.2	1090.4	1090.6
162.5°	1109.4	1109.4	1109.4	1109.4	1109.4	1109.4	1109.5	1109.7	1110.0	1110.2	1110.4
165°	1128.3	1128.1	1127.9	1127.6	1127.4	1127.3	1127.3	1127.3	1127.3	1127.3	1127.3
167.5°	1145.2	1144.5	1143.9	1143.2	1142.5	1142.2	1142.2	1142.2	1142.2	1142.2	1142.2
170°	1158.1	1157.4	1156.8	1156.1	1155.4	1155.1	1155.0	1154.8	1154.5	1154.3	1154.1
172.5°	1167.0	1166.3	1165.7	1165.0	1164.3	1164.0	1163.9	1163.7	1163.4	1163.2	1163.0
175°	1173.9	1173.3	1172.6	1172.0	1171.3	1171.0	1170.8	1170.3	1169.9	1169.4	1169.0
177.5°	1177.9	1177.2	1176.6	1175.9	1175.2	1174.9	1174.7	1174.2	1173.8	1173.3	1172.9
180°	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9

TEST NUMBER: P1010229

CATALOG NUMBER: S122RDIP-B675D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1535.7	1537.7	1540.8	1555.3	1557.3	1561.4	1559.4	1559.4	1560.4	1558.3	1559.4
5°	1601.6	1604.7	1620.2	1637.7	1641.8	1637.7	1642.9	1650.1	1650.1	1650.1	1648.0
7.5°	1663.5	1674.8	1692.3	1718.1	1723.3	1728.4	1737.7	1731.5	1733.6	1742.8	1739.7
10°	1723.3	1739.7	1759.3	1781.0	1792.3	1799.5	1803.6	1812.9	1834.6	1809.8	1819.1
12.5°	1779.9	1803.6	1824.3	1848.0	1856.2	1865.5	1868.6	1876.8	1876.8	1875.8	1883.0
15°	1817.0	1838.7	1857.2	1872.7	1874.8	1872.7	1870.6	1871.7	1874.8	1862.4	1869.6
17.5°	1825.3	1827.3	1833.5	1827.3	1828.4	1806.7	1794.4	1791.3	1762.4	1763.4	1787.2
20°	1785.1	1750.1	1740.8	1706.8	1686.1	1630.5	1628.4	1613.0	1552.2	1570.7	1566.6
22.5°	1674.8	1615.0	1535.7	1496.5	1476.9	1418.2	1372.8	1340.9	1319.2	1297.6	1288.3
25°	1529.5	1432.6	1320.3	1243.0	1231.6	1177.0	1093.5	1054.4	1008.0	993.6	1018.3
27.5°	1341.9	1216.2	1089.4	970.9	949.2	899.8	857.5	829.7	776.1	773.0	775.1
30°	1087.3	960.6	854.4	777.1	723.5	700.8	673.0	652.4	630.8	639.0	641.1
32.5°	893.6	773.0	674.0	632.8	608.1	593.7	570.0	556.6	547.3	544.2	543.2
35°	710.1	629.7	585.4	545.2	530.8	520.5	503.0	496.8	488.5	489.6	489.6
37.5°	608.1	541.1	508.1	487.5	474.1	468.9	457.6	451.4	446.3	444.2	447.3
40°	524.6	478.2	457.6	439.1	427.7	425.7	419.5	412.3	406.1	407.1	410.2
42.5°	463.8	437.0	412.3	397.8	389.6	386.5	381.3	376.2	376.2	373.1	372.1
45°	415.4	393.7	373.1	359.7	354.5	350.4	344.2	343.2	339.1	340.1	341.1
47.5°	372.1	354.5	339.1	325.7	320.5	319.5	313.3	309.2	309.2	308.2	307.1
50°	332.9	315.4	302.0	294.8	287.6	285.5	284.5	283.4	281.4	281.4	282.4
52.5°	301.0	283.4	273.1	266.9	262.8	260.8	260.8	259.7	259.7	259.7	258.7
55°	265.9	251.5	243.2	241.2	239.1	238.1	237.1	235.0	234.0	236.0	234.0
57.5°	232.9	227.8	220.6	218.5	213.3	213.3	210.3	208.2	206.1	208.2	208.2
60°	207.2	199.9	195.8	189.6	185.5	181.4	176.2	175.2	173.1	172.1	171.1
62.5°	180.4	174.2	163.9	154.6	148.4	144.3	142.2	141.2	141.2	140.2	140.2
65°	150.5	136.0	130.9	127.8	126.8	125.7	123.7	122.6	123.7	122.6	123.7
67.5°	117.5	115.4	112.3	110.3	109.2	108.2	108.2	107.2	107.2	107.2	107.2
70°	102.0	96.9	95.9	93.8	93.8	92.8	92.8	92.8	92.8	91.7	93.8
72.5°	84.5	81.4	80.4	79.4	79.4	79.4	78.3	78.3	78.3	77.3	78.3
75°	69.1	68.0	66.0	66.0	64.9	66.0	64.9	64.9	63.9	64.9	64.9
77.5°	55.7	54.6	53.6	53.6	52.6	52.6	52.6	52.6	52.6	52.6	53.6
80°	42.3	41.2	40.2	41.2	40.2	41.2	40.2	40.2	41.2	40.2	40.2
82.5°	30.9	29.9	29.9	28.9	28.9	28.9	28.9	28.9	28.9	28.9	28.9
85°	18.6	17.5	17.5	18.6	17.5	18.6	17.5	17.5	17.5	18.6	18.6
87.5°	8.2	9.3	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	9.3
90°	34.3	33.8	33.4	32.9	32.7	32.8	33.0	33.3	33.5	33.7	33.5
92.5°	31.0	31.2	31.5	31.7	31.8	31.8	31.8	31.8	31.8	31.8	31.8
95°	63.5	63.5	63.5	63.5	63.5	63.3	62.8	62.4	61.9	61.5	61.9
97.5°	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2
100°	136.9	136.9	136.9	136.9	136.9	136.8	136.6	136.4	136.2	136.0	136.2
102.5°	177.8	178.0	178.3	178.5	178.6	178.5	178.3	178.0	177.8	177.6	177.8
105°	218.7	219.2	219.6	220.1	220.3	220.3	220.3	220.3	220.3	220.3	220.3
107.5°	263.2	263.4	263.7	263.9	264.0	263.4	262.3	261.2	260.1	259.0	260.1
110°	308.6	308.6	308.6	308.6	308.6	308.3	307.6	306.9	306.3	305.6	306.3

TEST NUMBER: P1010229

CATALOG NUMBER: S122RDIP-B675D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	354.6	354.0	353.3	352.6	352.3	352.1	351.6	351.2	350.7	350.3	350.7
115°	400.7	400.5	400.2	400.0	399.9	399.6	398.9	398.2	397.6	396.9	397.6
117.5°	445.9	445.3	444.6	443.9	443.6	443.3	442.6	441.9	441.3	440.6	441.3
120°	490.2	490.2	490.2	490.2	490.2	489.9	489.2	488.5	487.9	487.2	487.9
122.5°	537.2	536.5	535.9	535.2	534.9	534.7	534.2	533.8	533.3	532.9	533.3
125°	582.8	582.2	581.5	580.8	580.5	580.4	580.2	579.9	579.7	579.5	579.7
127.5°	627.3	626.4	625.5	624.6	624.2	623.9	623.2	622.5	621.9	621.2	621.9
130°	672.4	671.9	671.5	671.0	670.8	670.4	669.5	668.6	667.8	666.9	667.8
132.5°	717.4	716.3	715.2	714.1	713.5	713.2	712.5	711.8	711.2	710.5	711.2
135°	759.9	759.7	759.4	759.2	759.1	758.8	758.1	757.5	756.8	756.2	756.8
137.5°	801.6	801.4	801.1	800.9	800.8	800.4	799.5	798.6	797.7	796.8	797.7
140°	843.5	843.5	843.5	843.5	843.5	843.1	842.2	841.3	840.4	839.5	840.4
142.5°	881.4	881.6	881.9	882.1	882.2	881.8	880.9	880.0	879.1	878.2	879.1
145°	920.1	920.3	920.6	920.8	920.9	920.5	919.6	918.7	917.8	916.9	917.8
147.5°	954.0	954.5	954.9	955.4	955.6	955.2	954.3	953.4	952.6	951.7	952.6
150°	986.1	986.7	987.4	988.1	988.4	988.1	987.4	986.7	986.1	985.4	986.1
152.5°	1018.0	1018.9	1019.8	1020.7	1021.1	1020.7	1019.8	1018.9	1018.0	1017.1	1018.0
155°	1044.0	1045.1	1046.2	1047.3	1047.9	1047.6	1046.9	1046.2	1045.6	1044.9	1045.6
157.5°	1069.3	1070.9	1072.4	1073.9	1074.7	1074.1	1073.0	1071.9	1070.8	1069.7	1070.8
160°	1091.9	1093.2	1094.5	1095.8	1096.5	1096.1	1095.2	1094.3	1093.5	1092.6	1093.5
162.5°	1112.0	1113.5	1115.1	1116.6	1117.4	1116.8	1115.7	1114.6	1113.5	1112.4	1113.5
165°	1128.8	1130.4	1131.9	1133.4	1134.2	1133.7	1132.6	1131.5	1130.4	1129.3	1130.4
167.5°	1143.7	1145.3	1146.8	1148.3	1149.1	1148.6	1147.5	1146.4	1145.3	1144.2	1145.3
170°	1155.6	1157.2	1158.7	1160.2	1161.0	1160.3	1159.0	1157.7	1156.4	1155.1	1156.4
172.5°	1164.6	1166.1	1167.7	1169.2	1170.0	1169.3	1168.0	1166.7	1165.3	1164.0	1165.3
175°	1170.5	1172.1	1173.6	1175.1	1175.9	1175.2	1173.9	1172.6	1171.3	1170.0	1171.3
177.5°	1174.2	1175.6	1176.9	1178.2	1178.9	1178.2	1176.9	1175.6	1174.2	1172.9	1174.2
180°	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9

TEST NUMBER: P1010229

CATALOG NUMBER: S122RDIP-B675D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1563.5	1556.3	1554.2	1556.3	1554.2	1555.3	1548.0	1521.2	1528.5	1517.1	1523.3
5°	1652.1	1646.0	1632.6	1630.5	1628.4	1626.4	1616.1	1592.4	1583.1	1567.6	1566.6
7.5°	1736.7	1736.7	1726.3	1719.1	1709.9	1702.6	1689.2	1654.2	1639.8	1621.2	1610.9
10°	1820.1	1793.3	1804.7	1797.5	1774.8	1770.7	1745.9	1725.3	1697.5	1678.9	1662.4
12.5°	1879.9	1871.7	1861.4	1855.2	1849.0	1835.6	1819.1	1766.5	1752.1	1715.0	1696.5
15°	1877.9	1872.7	1875.8	1875.8	1873.7	1870.6	1857.2	1819.1	1794.4	1758.3	1726.3
17.5°	1776.8	1790.2	1803.6	1812.9	1833.5	1842.8	1855.2	1832.5	1817.0	1786.1	1752.1
20°	1600.6	1633.6	1672.8	1681.0	1699.5	1754.2	1778.9	1798.5	1804.7	1794.4	1766.5
22.5°	1355.3	1383.1	1478.0	1475.9	1502.7	1567.6	1639.8	1698.5	1744.9	1770.7	1760.4
25°	1061.6	1100.7	1151.2	1189.4	1277.0	1373.9	1463.5	1557.3	1637.7	1708.8	1726.3
27.5°	802.9	854.4	894.6	945.1	989.4	1103.8	1219.3	1365.6	1459.4	1594.4	1664.5
30°	649.3	673.0	713.2	736.9	758.6	846.2	977.1	1121.4	1286.3	1441.9	1562.5
32.5°	554.5	571.0	600.9	611.2	633.9	692.6	775.1	907.0	1077.0	1265.6	1424.4
35°	497.8	515.3	521.5	530.8	549.3	586.4	643.1	739.0	892.5	1077.0	1266.7
37.5°	449.4	458.6	476.2	482.3	488.5	516.4	554.5	621.5	723.5	875.0	1085.3
40°	415.4	420.5	429.8	434.9	439.1	458.6	492.7	538.0	613.2	728.7	922.4
42.5°	379.3	385.5	391.6	397.8	403.0	418.4	439.1	482.3	532.8	620.5	760.6
45°	344.2	348.4	355.6	359.7	366.9	379.3	397.8	427.7	473.1	528.7	642.1
47.5°	312.3	317.4	320.5	325.7	330.8	344.2	361.8	381.3	418.4	473.1	555.5
50°	283.4	289.6	293.7	294.8	298.9	311.3	325.7	347.3	371.0	413.3	485.4
52.5°	262.8	263.8	266.9	271.1	270.0	277.2	290.6	307.1	331.9	365.9	418.4
55°	239.1	242.2	244.3	245.3	245.3	251.5	258.7	274.2	293.7	321.6	365.9
57.5°	209.2	212.3	218.5	220.6	223.7	226.7	229.8	240.1	256.6	283.4	319.5
60°	178.3	180.4	186.5	190.7	192.7	201.0	205.1	213.3	222.6	242.2	276.2
62.5°	143.3	145.3	148.4	152.5	156.7	169.0	179.3	187.6	194.8	208.2	236.0
65°	124.7	125.7	127.8	128.8	129.9	135.0	144.3	155.6	169.0	179.3	195.8
67.5°	108.2	109.2	110.3	112.3	113.4	114.4	118.5	121.6	135.0	149.4	161.8
70°	92.8	94.8	95.9	95.9	96.9	98.9	101.0	105.1	109.2	116.5	131.9
72.5°	78.3	79.4	81.4	81.4	81.4	83.5	85.5	87.6	89.7	93.8	100.0
75°	64.9	67.0	67.0	67.0	68.0	68.0	70.1	72.1	74.2	77.3	79.4
77.5°	53.6	53.6	53.6	53.6	54.6	54.6	55.7	57.7	58.7	59.8	61.8
80°	40.2	41.2	41.2	41.2	42.3	42.3	42.3	44.3	45.3	45.3	47.4
82.5°	29.9	29.9	29.9	30.9	29.9	30.9	30.9	32.0	30.9	32.0	33.0
85°	18.6	18.6	18.6	19.6	19.6	19.6	19.6	19.6	19.6	19.6	20.6
87.5°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	10.3	9.3	9.3
90°	33.3	33.0	32.8	32.7	32.9	33.4	33.8	34.3	34.7	29.9	25.0
92.5°	31.8	31.8	31.8	31.8	31.7	31.5	31.2	31.0	30.8	30.6	30.4
95°	62.4	62.8	63.3	63.5	63.5	63.5	63.5	63.5	63.5	63.1	62.6
97.5°	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	98.3	97.5
100°	136.4	136.6	136.8	136.9	136.9	136.9	136.9	136.9	136.9	136.3	135.6
102.5°	178.0	178.3	178.5	178.6	178.5	178.3	178.0	177.8	177.6	176.7	175.9
105°	220.3	220.3	220.3	220.3	220.1	219.6	219.2	218.7	218.3	217.9	217.4
107.5°	261.2	262.3	263.4	264.0	263.9	263.7	263.4	263.2	263.0	263.0	263.0
110°	306.9	307.6	308.3	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6

TEST NUMBER: P1010229

CATALOG NUMBER: S122RDIP-B675D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	351.2	351.6	352.1	352.3	352.6	353.3	354.0	354.6	355.3	355.5	355.7
115°	398.2	398.9	399.6	399.9	400.0	400.2	400.5	400.7	400.9	401.3	401.8
117.5°	441.9	442.6	443.3	443.6	443.9	444.6	445.3	445.9	446.6	447.7	448.8
120°	488.5	489.2	489.9	490.2	490.2	490.2	490.2	490.2	490.2	492.0	493.8
122.5°	533.8	534.2	534.7	534.9	535.2	535.9	536.5	537.2	537.8	538.9	540.0
125°	579.9	580.2	580.4	580.5	580.8	581.5	582.2	582.8	583.5	584.2	584.8
127.5°	622.5	623.2	623.9	624.2	624.6	625.5	626.4	627.3	628.2	629.1	629.9
130°	668.6	669.5	670.4	670.8	671.0	671.5	671.9	672.4	672.8	673.2	673.7
132.5°	711.8	712.5	713.2	713.5	714.1	715.2	716.3	717.4	718.5	718.3	718.1
135°	757.5	758.1	758.8	759.1	759.2	759.4	759.7	759.9	760.1	759.7	759.2
137.5°	798.6	799.5	800.4	800.8	800.9	801.1	801.4	801.6	801.8	801.4	800.9
140°	841.3	842.2	843.1	843.5	843.5	843.5	843.5	843.5	843.5	842.4	841.3
142.5°	880.0	880.9	881.8	882.2	882.1	881.9	881.6	881.4	881.2	880.5	879.9
145°	918.7	919.6	920.5	920.9	920.8	920.6	920.3	920.1	919.9	918.6	917.2
147.5°	953.4	954.3	955.2	955.6	955.4	954.9	954.5	954.0	953.6	952.7	951.9
150°	986.7	987.4	988.1	988.4	988.1	987.4	986.7	986.1	985.4	984.5	983.6
152.5°	1018.9	1019.8	1020.7	1021.1	1020.7	1019.8	1018.9	1018.0	1017.1	1016.0	1014.9
155°	1046.2	1046.9	1047.6	1047.9	1047.3	1046.2	1045.1	1044.0	1042.9	1042.3	1041.6
157.5°	1071.9	1073.0	1074.1	1074.7	1073.9	1072.4	1070.9	1069.3	1067.8	1067.4	1066.9
160°	1094.3	1095.2	1096.1	1096.5	1095.8	1094.5	1093.2	1091.9	1090.6	1090.4	1090.2
162.5°	1114.6	1115.7	1116.8	1117.4	1116.6	1115.1	1113.5	1112.0	1110.4	1110.2	1110.0
165°	1131.5	1132.6	1133.7	1134.2	1133.4	1131.9	1130.4	1128.8	1127.3	1127.3	1127.3
167.5°	1146.4	1147.5	1148.6	1149.1	1148.3	1146.8	1145.3	1143.7	1142.2	1142.2	1142.2
170°	1157.7	1159.0	1160.3	1161.0	1160.2	1158.7	1157.2	1155.6	1154.1	1154.3	1154.5
172.5°	1166.7	1168.0	1169.3	1170.0	1169.2	1167.7	1166.1	1164.6	1163.0	1163.2	1163.4
175°	1172.6	1173.9	1175.2	1175.9	1175.1	1173.6	1172.1	1170.5	1169.0	1169.4	1169.9
177.5°	1175.6	1176.9	1178.2	1178.9	1178.2	1176.9	1175.6	1174.2	1172.9	1173.3	1173.8
180°	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9

TEST NUMBER: P1010229

CATALOG NUMBER: S122RDIP-B675D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1514.0	1508.9	1508.9	1505.8	1505.8	1489.3	1489.3	1494.4	1488.3	1481.0	1470.7
5°	1553.2	1541.9	1538.8	1534.6	1521.2	1500.6	1492.4	1489.3	1476.9	1461.5	1443.9
7.5°	1590.3	1571.7	1562.5	1553.2	1535.7	1506.8	1490.3	1479.0	1460.4	1436.7	1414.1
10°	1626.4	1602.7	1579.0	1567.6	1542.9	1506.8	1483.1	1464.6	1437.8	1405.8	1373.9
12.5°	1659.4	1609.9	1605.8	1583.1	1547.0	1505.8	1469.7	1442.9	1408.9	1371.8	1334.7
15°	1688.2	1637.7	1613.0	1592.4	1545.0	1493.4	1455.3	1422.3	1377.0	1334.7	1289.3
17.5°	1702.6	1648.0	1631.5	1597.5	1549.1	1482.1	1430.5	1390.4	1340.9	1290.4	1238.8
20°	1717.1	1653.2	1626.4	1602.7	1536.7	1460.4	1402.7	1356.3	1301.7	1241.9	1185.3
22.5°	1724.3	1653.2	1621.2	1588.2	1524.3	1436.7	1368.7	1314.1	1250.2	1189.4	1121.4
25°	1711.9	1647.0	1608.9	1574.8	1502.7	1407.9	1329.5	1267.7	1199.7	1130.6	1061.6
27.5°	1681.0	1632.6	1588.2	1553.2	1472.8	1370.8	1288.3	1218.2	1148.1	1070.8	1000.8
30°	1623.3	1601.6	1566.6	1527.4	1439.8	1337.8	1239.9	1167.7	1090.4	1013.1	940.0
32.5°	1533.6	1552.2	1529.5	1495.5	1400.7	1292.4	1188.3	1115.2	1030.7	947.2	880.2
35°	1424.4	1490.3	1478.0	1454.3	1359.4	1244.0	1139.9	1051.3	966.8	882.2	815.2
37.5°	1304.8	1404.8	1415.1	1400.7	1312.0	1194.5	1080.1	993.6	907.0	821.4	753.4
40°	1140.9	1294.5	1327.5	1333.7	1262.6	1134.8	1015.2	930.7	845.1	761.7	679.2
42.5°	990.5	1184.2	1225.4	1251.2	1199.7	1076.0	955.4	861.6	777.1	701.9	619.4
45°	849.3	1051.3	1118.3	1151.2	1128.6	1009.0	884.3	796.7	719.4	650.3	571.0
47.5°	703.9	907.0	1000.8	1053.3	1053.3	941.0	816.3	729.7	655.5	596.7	526.7
50°	607.1	776.1	873.0	942.0	960.6	871.9	754.4	669.9	599.8	535.9	482.3
52.5°	517.4	668.9	749.3	821.4	875.0	797.7	685.4	609.1	540.1	480.3	438.0
55°	447.3	560.7	633.9	713.2	773.0	722.5	618.4	544.2	484.4	434.9	398.9
57.5°	380.3	479.3	539.0	609.1	673.0	634.9	551.4	487.5	434.9	391.6	359.7
60°	323.6	404.0	450.4	505.0	584.4	557.6	488.5	429.8	387.5	348.4	321.6
62.5°	275.2	339.1	378.3	417.4	489.6	477.2	423.6	378.3	342.2	309.2	286.5
65°	225.7	278.3	309.2	343.2	400.9	406.1	362.8	330.8	297.9	269.0	248.4
67.5°	182.4	223.7	251.5	280.3	326.7	341.1	311.3	284.5	256.6	232.9	214.4
70°	147.4	176.2	196.9	219.5	257.7	275.2	259.7	241.2	218.5	198.9	182.4
72.5°	116.5	135.0	147.4	164.9	195.8	213.3	212.3	195.8	179.3	165.9	152.5
75°	85.5	100.0	110.3	121.6	146.4	162.8	167.0	159.8	143.3	133.0	122.6
77.5°	64.9	73.2	78.3	86.6	104.1	118.5	124.7	122.6	111.3	103.1	95.9
80°	49.5	51.5	53.6	56.7	71.1	84.5	88.6	87.6	81.4	78.3	70.1
82.5°	35.0	36.1	37.1	38.1	43.3	54.6	58.7	60.8	55.7	52.6	45.3
85°	20.6	21.6	21.6	23.7	24.7	27.8	35.0	35.0	34.0	29.9	28.9
87.5°	10.3	10.3	9.3	9.3	10.3	11.3	13.4	15.5	13.4	12.4	11.3
90°	20.2	15.3	12.9	11.6	8.9	6.3	3.6	1.0	3.6	6.3	8.9
92.5°	30.1	29.9	29.8	28.9	27.1	25.4	23.6	21.8	23.6	25.4	27.1
95°	62.2	61.7	61.5	60.4	58.2	56.0	53.8	51.6	53.8	56.0	58.2
97.5°	96.6	95.7	95.3	94.3	92.3	90.3	88.3	86.3	88.3	90.3	92.3
100°	135.0	134.3	134.0	133.1	131.3	129.6	127.8	126.0	127.8	129.6	131.3
102.5°	175.0	174.1	173.7	173.0	171.7	170.4	169.0	167.7	169.0	170.4	171.7
105°	217.0	216.5	216.3	216.0	215.3	214.7	214.0	213.4	214.0	214.7	215.3
107.5°	263.0	263.0	263.0	262.6	261.7	260.8	259.9	259.0	259.9	260.8	261.7
110°	308.6	308.6	308.6	307.9	306.6	305.3	304.0	302.7	304.0	305.3	306.6

TEST NUMBER: P1010229

CATALOG NUMBER: S122RDIP-B675D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	355.9	356.1	356.2	355.5	354.2	352.9	351.6	350.3	351.6	352.9	354.2
115°	402.2	402.7	402.9	402.2	400.9	399.6	398.2	396.9	398.2	399.6	400.9
117.5°	449.9	451.0	451.5	450.6	448.9	447.1	445.4	443.6	445.4	447.1	448.9
120°	495.5	497.3	498.2	497.3	495.5	493.8	492.0	490.2	492.0	493.8	495.5
122.5°	541.1	542.2	542.8	541.7	539.5	537.3	535.1	532.9	535.1	537.3	539.5
125°	585.5	586.2	586.5	585.5	583.5	581.5	579.5	577.5	579.5	581.5	583.5
127.5°	630.8	631.7	632.1	630.9	628.5	626.0	623.6	621.2	623.6	626.0	628.5
130°	674.1	674.6	674.8	673.4	670.5	667.6	664.8	661.9	664.8	667.6	670.5
132.5°	717.8	717.6	717.5	716.4	714.2	711.9	709.7	707.5	709.7	711.9	714.2
135°	758.8	758.3	758.1	756.9	754.5	752.0	749.6	747.2	749.6	752.0	754.5
137.5°	800.5	800.0	799.8	798.8	796.8	794.9	792.9	790.9	792.9	794.9	796.8
140°	840.2	839.1	838.5	837.5	835.5	833.6	831.6	829.6	831.6	833.6	835.5
142.5°	879.2	878.5	878.2	877.2	875.2	873.3	871.3	869.3	871.3	873.3	875.2
145°	915.9	914.6	913.9	913.1	911.6	910.1	908.5	907.0	908.5	910.1	911.6
147.5°	951.0	950.1	949.7	948.7	946.7	944.7	942.7	940.7	942.7	944.7	946.7
150°	982.7	981.8	981.4	980.7	979.4	978.1	976.8	975.5	976.8	978.1	979.4
152.5°	1013.8	1012.7	1012.2	1011.5	1010.2	1008.9	1007.5	1006.2	1007.5	1008.9	1010.2
155°	1041.0	1040.3	1040.0	1039.7	1039.0	1038.3	1037.7	1037.0	1037.7	1038.3	1039.0
157.5°	1066.5	1066.0	1065.8	1065.6	1065.1	1064.7	1064.2	1063.8	1064.2	1064.7	1065.1
160°	1089.9	1089.7	1089.6	1089.4	1088.9	1088.5	1088.0	1087.6	1088.0	1088.5	1088.9
162.5°	1109.7	1109.5	1109.4	1109.4	1109.4	1109.4	1109.4	1109.4	1109.4	1109.4	1109.4
165°	1127.3	1127.3	1127.3	1127.4	1127.6	1127.9	1128.1	1128.3	1128.1	1127.9	1127.6
167.5°	1142.2	1142.2	1142.2	1142.5	1143.2	1143.9	1144.5	1145.2	1144.5	1143.9	1143.2
170°	1154.8	1155.0	1155.1	1155.4	1156.1	1156.8	1157.4	1158.1	1157.4	1156.8	1156.1
172.5°	1163.7	1163.9	1164.0	1164.3	1165.0	1165.7	1166.3	1167.0	1166.3	1165.7	1165.0
175°	1170.3	1170.8	1171.0	1171.3	1172.0	1172.6	1173.3	1173.9	1173.3	1172.6	1172.0
177.5°	1174.2	1174.7	1174.9	1175.2	1175.9	1176.6	1177.2	1177.9	1177.2	1176.6	1175.9
180°	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9

TEST NUMBER: P1010229

CATALOG NUMBER: S122RDIP-B675D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1466.6	1467.7	1470.7	1461.5	1447.0	1440.9	1422.3	1419.2	1416.1	1416.1	1419.2
5°	1433.6	1429.5	1430.5	1413.0	1392.4	1380.0	1354.3	1358.4	1345.0	1336.8	1338.8
7.5°	1397.6	1386.2	1385.2	1362.5	1336.8	1314.1	1287.3	1281.1	1268.7	1254.3	1248.1
10°	1352.2	1344.0	1328.5	1302.7	1269.8	1251.2	1215.1	1193.5	1190.4	1168.8	1160.5
12.5°	1305.8	1291.4	1275.9	1239.9	1202.8	1172.9	1146.1	1122.4	1105.9	1087.3	1075.0
15°	1252.2	1234.7	1217.2	1179.1	1135.8	1105.9	1065.7	1030.7	982.2	944.1	922.4
17.5°	1193.5	1173.9	1150.2	1108.0	1065.7	1024.5	950.3	909.0	875.0	852.4	839.0
20°	1132.7	1111.0	1087.3	1045.1	971.9	899.8	858.5	826.6	806.0	783.3	766.8
22.5°	1068.8	1046.1	1020.3	954.4	877.1	826.6	794.6	764.7	734.9	722.5	714.2
25°	1009.0	988.4	955.4	865.7	804.9	758.6	722.5	702.9	687.4	671.0	655.5
27.5°	947.2	909.0	862.7	787.4	749.3	701.9	676.1	661.7	634.9	623.5	616.3
30°	873.0	830.7	786.4	732.8	688.5	655.5	631.8	608.1	592.6	581.3	568.9
32.5°	797.7	757.5	729.7	674.0	641.1	607.1	584.4	570.0	547.3	540.1	534.9
35°	732.8	698.8	674.0	628.7	597.8	566.9	550.4	528.7	514.3	500.9	492.7
37.5°	668.9	650.3	624.6	586.4	553.5	528.7	506.1	498.8	479.3	472.0	463.8
40°	624.6	596.7	575.1	542.1	514.3	487.5	473.1	456.6	443.2	431.8	428.8
42.5°	571.0	550.4	538.0	501.9	473.1	457.6	440.1	421.5	411.2	402.0	390.6
45°	530.8	512.2	494.7	465.9	440.1	420.5	405.0	392.7	375.2	371.0	353.5
47.5°	488.5	470.0	456.6	427.7	404.0	385.5	374.1	357.6	343.2	333.9	325.7
50°	446.3	430.8	418.4	393.7	373.1	353.5	338.1	321.6	315.4	299.9	294.8
52.5°	406.1	395.8	382.4	358.7	338.1	321.6	305.1	291.7	282.4	274.2	268.0
55°	372.1	355.6	349.4	323.6	306.1	288.6	274.2	265.9	254.6	249.4	244.3
57.5°	333.9	324.7	314.3	294.8	275.2	258.7	248.4	236.0	229.8	223.7	219.5
60°	301.0	287.6	279.3	262.8	245.3	229.8	220.6	211.3	203.0	197.9	189.6
62.5°	262.8	252.5	247.4	229.8	215.4	201.0	192.7	183.5	177.3	168.0	157.7
65°	229.8	221.6	215.4	201.0	187.6	174.2	165.9	154.6	146.4	141.2	140.2
67.5°	201.0	194.8	185.5	172.1	158.7	148.4	139.1	129.9	128.8	126.8	126.8
70°	169.0	162.8	157.7	143.3	131.9	120.6	118.5	115.4	112.3	111.3	109.2
72.5°	141.2	136.0	129.9	117.5	106.2	103.1	101.0	98.9	95.9	94.8	93.8
75°	114.4	107.2	103.1	91.7	88.6	86.6	84.5	81.4	79.4	78.3	76.3
77.5°	87.6	80.4	80.4	74.2	72.1	69.1	67.0	64.9	63.9	61.8	61.8
80°	61.8	61.8	59.8	56.7	53.6	52.6	49.5	48.4	47.4	48.4	46.4
82.5°	45.3	41.2	41.2	39.2	37.1	36.1	34.0	34.0	33.0	33.0	33.0
85°	25.8	25.8	24.7	22.7	21.6	21.6	20.6	20.6	19.6	19.6	18.6
87.5°	10.3	9.3	10.3	9.3	9.3	8.2	8.2	8.2	7.2	8.2	7.2
90°	11.6	12.9	15.3	20.2	25.0	29.9	34.7	34.3	33.8	33.4	32.9
92.5°	28.9	29.8	29.9	30.1	30.4	30.6	30.8	31.0	31.2	31.5	31.7
95°	60.4	61.5	61.7	62.2	62.6	63.1	63.5	63.5	63.5	63.5	63.5
97.5°	94.3	95.3	95.7	96.6	97.5	98.3	99.2	99.2	99.2	99.2	99.2
100°	133.1	134.0	134.3	135.0	135.6	136.3	136.9	136.9	136.9	136.9	136.9
102.5°	173.0	173.7	174.1	175.0	175.9	176.7	177.6	177.8	178.0	178.3	178.5
105°	216.0	216.3	216.5	217.0	217.4	217.9	218.3	218.7	219.2	219.6	220.1
107.5°	262.6	263.0	263.0	263.0	263.0	263.0	263.0	263.2	263.4	263.7	263.9
110°	307.9	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6

TEST NUMBER: P1010229

CATALOG NUMBER: S122RDIP-B675D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	355.5	356.2	356.1	355.9	355.7	355.5	355.3	354.6	354.0	353.3	352.6
115°	402.2	402.9	402.7	402.2	401.8	401.3	400.9	400.7	400.5	400.2	400.0
117.5°	450.6	451.5	451.0	449.9	448.8	447.7	446.6	445.9	445.3	444.6	443.9
120°	497.3	498.2	497.3	495.5	493.8	492.0	490.2	490.2	490.2	490.2	490.2
122.5°	541.7	542.8	542.2	541.1	540.0	538.9	537.8	537.2	536.5	535.9	535.2
125°	585.5	586.5	586.2	585.5	584.8	584.2	583.5	582.8	582.2	581.5	580.8
127.5°	630.9	632.1	631.7	630.8	629.9	629.1	628.2	627.3	626.4	625.5	624.6
130°	673.4	674.8	674.6	674.1	673.7	673.2	672.8	672.4	671.9	671.5	671.0
132.5°	716.4	717.5	717.6	717.8	718.1	718.3	718.5	717.4	716.3	715.2	714.1
135°	756.9	758.1	758.3	758.8	759.2	759.7	760.1	759.9	759.7	759.4	759.2
137.5°	798.8	799.8	800.0	800.5	800.9	801.4	801.8	801.6	801.4	801.1	800.9
140°	837.5	838.5	839.1	840.2	841.3	842.4	843.5	843.5	843.5	843.5	843.5
142.5°	877.2	878.2	878.5	879.2	879.9	880.5	881.2	881.4	881.6	881.9	882.1
145°	913.1	913.9	914.6	915.9	917.2	918.6	919.9	920.1	920.3	920.6	920.8
147.5°	948.7	949.7	950.1	951.0	951.9	952.7	953.6	954.0	954.5	954.9	955.4
150°	980.7	981.4	981.8	982.7	983.6	984.5	985.4	986.1	986.7	987.4	988.1
152.5°	1011.5	1012.2	1012.7	1013.8	1014.9	1016.0	1017.1	1018.0	1018.9	1019.8	1020.7
155°	1039.7	1040.0	1040.3	1041.0	1041.6	1042.3	1042.9	1044.0	1045.1	1046.2	1047.3
157.5°	1065.6	1065.8	1066.0	1066.5	1066.9	1067.4	1067.8	1069.3	1070.9	1072.4	1073.9
160°	1089.4	1089.6	1089.7	1089.9	1090.2	1090.4	1090.6	1091.9	1093.2	1094.5	1095.8
162.5°	1109.4	1109.4	1109.5	1109.7	1110.0	1110.2	1110.4	1112.0	1113.5	1115.1	1116.6
165°	1127.4	1127.3	1127.3	1127.3	1127.3	1127.3	1127.3	1128.8	1130.4	1131.9	1133.4
167.5°	1142.5	1142.2	1142.2	1142.2	1142.2	1142.2	1142.2	1143.7	1145.3	1146.8	1148.3
170°	1155.4	1155.1	1155.0	1154.8	1154.5	1154.3	1154.1	1155.6	1157.2	1158.7	1160.2
172.5°	1164.3	1164.0	1163.9	1163.7	1163.4	1163.2	1163.0	1164.6	1166.1	1167.7	1169.2
175°	1171.3	1171.0	1170.8	1170.3	1169.9	1169.4	1169.0	1170.5	1172.1	1173.6	1175.1
177.5°	1175.2	1174.9	1174.7	1174.2	1173.8	1173.3	1172.9	1174.2	1175.6	1176.9	1178.2
180°	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9

TEST NUMBER: P1010229

CATALOG NUMBER: S122RDIP-B675D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1419.2	1417.1	1411.0	1413.0	1409.9	1409.9	1407.9	1407.9	1407.9	1413.0	1409.9
5°	1341.9	1334.7	1327.5	1324.4	1321.3	1318.2	1318.2	1317.2	1326.5	1324.4	1332.6
7.5°	1246.1	1244.0	1229.6	1229.6	1224.4	1222.4	1227.5	1228.5	1229.6	1231.6	1236.8
10°	1160.5	1155.4	1134.8	1136.8	1133.7	1129.6	1132.7	1130.6	1137.8	1139.9	1137.8
12.5°	1059.5	1050.2	1027.6	1016.2	1003.9	994.6	1005.9	997.7	1026.5	1034.8	1057.5
15°	925.5	908.0	892.5	892.5	881.2	873.0	878.1	887.4	893.6	902.9	907.0
17.5°	835.9	828.6	816.3	809.1	806.0	802.9	802.9	807.0	820.4	819.4	827.6
20°	759.6	755.5	749.3	740.0	736.9	734.9	734.9	734.9	744.1	752.4	757.5
22.5°	707.0	703.9	699.8	687.4	681.3	679.2	684.4	687.4	694.7	700.8	706.0
25°	654.5	647.3	640.0	635.9	632.8	632.8	634.9	635.9	639.0	642.1	648.3
27.5°	611.2	606.0	595.7	584.4	584.4	581.3	583.4	585.4	592.6	602.9	608.1
30°	562.7	561.7	557.6	553.5	549.3	547.3	551.4	554.5	555.5	560.7	560.7
32.5°	527.7	520.5	513.3	509.1	507.1	506.1	507.1	511.2	511.2	517.4	524.6
35°	492.7	488.5	481.3	474.1	472.0	466.9	471.0	475.1	482.3	485.4	488.5
37.5°	454.5	449.4	446.3	444.2	440.1	441.1	438.0	444.2	450.4	449.4	451.4
40°	425.7	416.4	407.1	406.1	405.0	404.0	404.0	405.0	409.2	413.3	419.5
42.5°	388.6	385.5	377.2	369.0	366.9	364.9	362.8	366.9	375.2	382.4	385.5
45°	350.4	346.3	344.2	338.1	333.9	332.9	330.8	336.0	343.2	346.3	348.4
47.5°	315.4	314.3	308.2	309.2	306.1	307.1	306.1	309.2	309.2	312.3	314.3
50°	291.7	288.6	285.5	283.4	280.3	280.3	279.3	280.3	284.5	288.6	287.6
52.5°	268.0	262.8	261.8	260.8	258.7	260.8	257.7	258.7	262.8	264.9	263.8
55°	240.1	239.1	237.1	235.0	234.0	232.9	232.9	232.9	237.1	240.1	241.2
57.5°	218.5	213.3	209.2	209.2	205.1	204.1	206.1	207.2	210.3	212.3	214.4
60°	188.6	186.5	180.4	177.3	171.1	170.1	170.1	174.2	179.3	186.5	188.6
62.5°	156.7	153.6	152.5	152.5	152.5	152.5	152.5	152.5	152.5	153.6	153.6
65°	139.1	140.2	139.1	138.1	139.1	139.1	138.1	138.1	138.1	139.1	140.2
67.5°	124.7	123.7	124.7	123.7	122.6	122.6	121.6	122.6	123.7	124.7	124.7
70°	108.2	108.2	107.2	108.2	107.2	106.2	105.1	105.1	107.2	108.2	108.2
72.5°	92.8	92.8	91.7	91.7	89.7	89.7	90.7	89.7	89.7	92.8	92.8
75°	77.3	76.3	75.2	75.2	74.2	74.2	74.2	73.2	75.2	75.2	76.3
77.5°	60.8	60.8	60.8	59.8	59.8	58.7	58.7	59.8	59.8	59.8	60.8
80°	46.4	46.4	46.4	45.3	44.3	44.3	44.3	44.3	44.3	45.3	44.3
82.5°	32.0	32.0	32.0	32.0	32.0	30.9	30.9	30.9	32.0	32.0	30.9
85°	19.6	18.6	19.6	19.6	18.6	19.6	18.6	18.6	17.5	17.5	18.6
87.5°	8.2	7.2	6.2	6.2	7.2	6.2	6.2	6.2	7.2	6.2	6.2
90°	32.7	32.8	33.0	33.3	33.5	33.7	33.5	33.3	33.0	32.8	32.7
92.5°	31.8	31.8	31.8	31.8	31.8	31.8	31.8	31.8	31.8	31.8	31.8
95°	63.5	63.3	62.8	62.4	61.9	61.5	61.9	62.4	62.8	63.3	63.5
97.5°	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2
100°	136.9	136.8	136.6	136.4	136.2	136.0	136.2	136.4	136.6	136.8	136.9
102.5°	178.6	178.5	178.3	178.0	177.8	177.6	177.8	178.0	178.3	178.5	178.6
105°	220.3	220.3	220.3	220.3	220.3	220.3	220.3	220.3	220.3	220.3	220.3
107.5°	264.0	263.4	262.3	261.2	260.1	259.0	260.1	261.2	262.3	263.4	264.0
110°	308.6	308.3	307.6	306.9	306.3	305.6	306.3	306.9	307.6	308.3	308.6

TEST NUMBER: P1010229

CATALOG NUMBER: S122RDIP-B675D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	352.3	352.1	351.6	351.2	350.7	350.3	350.7	351.2	351.6	352.1	352.3
115°	399.9	399.6	398.9	398.2	397.6	396.9	397.6	398.2	398.9	399.6	399.9
117.5°	443.6	443.3	442.6	441.9	441.3	440.6	441.3	441.9	442.6	443.3	443.6
120°	490.2	489.9	489.2	488.5	487.9	487.2	487.9	488.5	489.2	489.9	490.2
122.5°	534.9	534.7	534.2	533.8	533.3	532.9	533.3	533.8	534.2	534.7	534.9
125°	580.5	580.4	580.2	579.9	579.7	579.5	579.7	579.9	580.2	580.4	580.5
127.5°	624.2	623.9	623.2	622.5	621.9	621.2	621.9	622.5	623.2	623.9	624.2
130°	670.8	670.4	669.5	668.6	667.8	666.9	667.8	668.6	669.5	670.4	670.8
132.5°	713.5	713.2	712.5	711.8	711.2	710.5	711.2	711.8	712.5	713.2	713.5
135°	759.1	758.8	758.1	757.5	756.8	756.2	756.8	757.5	758.1	758.8	759.1
137.5°	800.8	800.4	799.5	798.6	797.7	796.8	797.7	798.6	799.5	800.4	800.8
140°	843.5	843.1	842.2	841.3	840.4	839.5	840.4	841.3	842.2	843.1	843.5
142.5°	882.2	881.8	880.9	880.0	879.1	878.2	879.1	880.0	880.9	881.8	882.2
145°	920.9	920.5	919.6	918.7	917.8	916.9	917.8	918.7	919.6	920.5	920.9
147.5°	955.6	955.2	954.3	953.4	952.6	951.7	952.6	953.4	954.3	955.2	955.6
150°	988.4	988.1	987.4	986.7	986.1	985.4	986.1	986.7	987.4	988.1	988.4
152.5°	1021.1	1020.7	1019.8	1018.9	1018.0	1017.1	1018.0	1018.9	1019.8	1020.7	1021.1
155°	1047.9	1047.6	1046.9	1046.2	1045.6	1044.9	1045.6	1046.2	1046.9	1047.6	1047.9
157.5°	1074.7	1074.1	1073.0	1071.9	1070.8	1069.7	1070.8	1071.9	1073.0	1074.1	1074.7
160°	1096.5	1096.1	1095.2	1094.3	1093.5	1092.6	1093.5	1094.3	1095.2	1096.1	1096.5
162.5°	1117.4	1116.8	1115.7	1114.6	1113.5	1112.4	1113.5	1114.6	1115.7	1116.8	1117.4
165°	1134.2	1133.7	1132.6	1131.5	1130.4	1129.3	1130.4	1131.5	1132.6	1133.7	1134.2
167.5°	1149.1	1148.6	1147.5	1146.4	1145.3	1144.2	1145.3	1146.4	1147.5	1148.6	1149.1
170°	1161.0	1160.3	1159.0	1157.7	1156.4	1155.1	1156.4	1157.7	1159.0	1160.3	1161.0
172.5°	1170.0	1169.3	1168.0	1166.7	1165.3	1164.0	1165.3	1166.7	1168.0	1169.3	1170.0
175°	1175.9	1175.2	1173.9	1172.6	1171.3	1170.0	1171.3	1172.6	1173.9	1175.2	1175.9
177.5°	1178.9	1178.2	1176.9	1175.6	1174.2	1172.9	1174.2	1175.6	1176.9	1178.2	1178.9
180°	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9

TEST NUMBER: P1010229

CATALOG NUMBER: S122RDIP-B675D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1413.0	1418.2	1416.1	1404.8	1416.1	1419.2	1425.4	1431.6	1435.7	1441.9	1447.0
5°	1324.4	1334.7	1340.9	1334.7	1355.3	1358.4	1372.8	1381.1	1393.4	1403.8	1412.0
7.5°	1240.9	1249.2	1261.5	1263.6	1275.9	1290.4	1311.0	1331.6	1351.2	1361.5	1370.8
10°	1151.2	1165.7	1184.2	1180.1	1198.7	1221.3	1243.0	1275.9	1292.4	1311.0	1327.5
12.5°	1061.6	1070.8	1095.6	1103.8	1130.6	1148.1	1178.0	1198.7	1239.9	1261.5	1275.9
15°	904.9	943.0	974.0	1011.1	1046.1	1079.1	1105.9	1143.0	1179.1	1195.6	1219.3
17.5°	833.8	851.3	869.9	888.4	933.8	992.5	1039.9	1080.1	1111.0	1132.7	1160.5
20°	759.6	777.1	797.7	815.2	843.1	885.3	944.1	1013.1	1050.2	1072.9	1099.7
22.5°	707.0	723.5	736.9	752.4	774.0	804.9	849.3	934.8	984.3	1012.1	1035.8
25°	650.3	671.0	685.4	696.7	714.2	748.3	784.3	832.8	921.4	943.0	976.0
27.5°	611.2	617.4	633.9	651.4	668.9	687.4	724.5	765.8	825.6	873.0	913.2
30°	564.8	580.3	595.7	602.9	618.4	645.2	667.9	712.2	758.6	795.7	844.1
32.5°	529.8	539.0	549.3	566.9	581.3	599.8	622.5	659.6	698.8	722.5	759.6
35°	490.6	496.8	518.4	525.6	540.1	558.6	581.3	610.1	652.4	671.0	697.8
37.5°	453.5	467.9	474.1	490.6	504.0	522.5	539.0	572.0	599.8	621.5	646.2
40°	424.6	430.8	442.2	456.6	467.9	482.3	503.0	526.7	556.6	574.1	595.7
42.5°	389.6	394.7	409.2	417.4	436.0	449.4	461.7	490.6	517.4	530.8	552.4
45°	351.5	363.8	373.1	389.6	399.9	416.4	431.8	452.5	477.2	492.7	505.0
47.5°	318.5	330.8	340.1	355.6	372.1	379.3	395.8	417.4	440.1	452.5	470.0
50°	291.7	295.8	313.3	320.5	338.1	352.5	363.8	382.4	407.1	414.3	428.8
52.5°	265.9	269.0	280.3	289.6	305.1	317.4	331.9	349.4	370.0	381.3	392.7
55°	243.2	245.3	250.4	260.8	271.1	286.5	299.9	316.4	333.9	346.3	356.6
57.5°	217.5	221.6	225.7	231.9	242.2	256.6	271.1	286.5	301.0	309.2	322.6
60°	187.6	193.8	201.0	208.2	215.4	225.7	242.2	256.6	270.0	277.2	287.6
62.5°	155.6	168.0	174.2	182.4	188.6	197.9	210.3	226.7	236.0	245.3	253.5
65°	140.2	141.2	142.2	150.5	161.8	171.1	182.4	194.8	209.2	215.4	221.6
67.5°	124.7	125.7	127.8	128.8	133.0	143.3	155.6	169.0	180.4	184.5	190.7
70°	109.2	109.2	113.4	114.4	115.4	116.5	126.8	140.2	150.5	155.6	162.8
72.5°	92.8	93.8	95.9	96.9	98.9	101.0	104.1	111.3	123.7	128.8	137.1
75°	76.3	77.3	78.3	79.4	82.5	83.5	86.6	90.7	95.9	102.0	107.2
77.5°	60.8	60.8	61.8	63.9	66.0	67.0	70.1	72.1	74.2	77.3	81.4
80°	45.3	46.4	46.4	48.4	48.4	49.5	50.5	53.6	55.7	57.7	59.8
82.5°	30.9	33.0	33.0	33.0	34.0	35.0	36.1	36.1	38.1	39.2	42.3
85°	18.6	19.6	19.6	19.6	18.6	20.6	20.6	21.6	21.6	21.6	22.7
87.5°	7.2	6.2	7.2	7.2	7.2	8.2	7.2	7.2	8.2	9.3	9.3
90°	32.9	33.4	33.8	34.3	34.7	29.9	25.0	20.2	15.3	12.9	11.6
92.5°	31.7	31.5	31.2	31.0	30.8	30.6	30.4	30.1	29.9	29.8	28.9
95°	63.5	63.5	63.5	63.5	63.5	63.1	62.6	62.2	61.7	61.5	60.4
97.5°	99.2	99.2	99.2	99.2	99.2	98.3	97.5	96.6	95.7	95.3	94.3
100°	136.9	136.9	136.9	136.9	136.9	136.3	135.6	135.0	134.3	134.0	133.1
102.5°	178.5	178.3	178.0	177.8	177.6	176.7	175.9	175.0	174.1	173.7	173.0
105°	220.1	219.6	219.2	218.7	218.3	217.9	217.4	217.0	216.5	216.3	216.0
107.5°	263.9	263.7	263.4	263.2	263.0	263.0	263.0	263.0	263.0	263.0	262.6
110°	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6	307.9

TEST NUMBER: P1010229

CATALOG NUMBER: S122RDIP-B675D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	352.6	353.3	354.0	354.6	355.3	355.5	355.7	355.9	356.1	356.2	355.5
115°	400.0	400.2	400.5	400.7	400.9	401.3	401.8	402.2	402.7	402.9	402.2
117.5°	443.9	444.6	445.3	445.9	446.6	447.7	448.8	449.9	451.0	451.5	450.6
120°	490.2	490.2	490.2	490.2	490.2	492.0	493.8	495.5	497.3	498.2	497.3
122.5°	535.2	535.9	536.5	537.2	537.8	538.9	540.0	541.1	542.2	542.8	541.7
125°	580.8	581.5	582.2	582.8	583.5	584.2	584.8	585.5	586.2	586.5	585.5
127.5°	624.6	625.5	626.4	627.3	628.2	629.1	629.9	630.8	631.7	632.1	630.9
130°	671.0	671.5	671.9	672.4	672.8	673.2	673.7	674.1	674.6	674.8	673.4
132.5°	714.1	715.2	716.3	717.4	718.5	718.3	718.1	717.8	717.6	717.5	716.4
135°	759.2	759.4	759.7	759.9	760.1	759.7	759.2	758.8	758.3	758.1	756.9
137.5°	800.9	801.1	801.4	801.6	801.8	801.4	800.9	800.5	800.0	799.8	798.8
140°	843.5	843.5	843.5	843.5	843.5	842.4	841.3	840.2	839.1	838.5	837.5
142.5°	882.1	881.9	881.6	881.4	881.2	880.5	879.9	879.2	878.5	878.2	877.2
145°	920.8	920.6	920.3	920.1	919.9	918.6	917.2	915.9	914.6	913.9	913.1
147.5°	955.4	954.9	954.5	954.0	953.6	952.7	951.9	951.0	950.1	949.7	948.7
150°	988.1	987.4	986.7	986.1	985.4	984.5	983.6	982.7	981.8	981.4	980.7
152.5°	1020.7	1019.8	1018.9	1018.0	1017.1	1016.0	1014.9	1013.8	1012.7	1012.2	1011.5
155°	1047.3	1046.2	1045.1	1044.0	1042.9	1042.3	1041.6	1041.0	1040.3	1040.0	1039.7
157.5°	1073.9	1072.4	1070.9	1069.3	1067.8	1067.4	1066.9	1066.5	1066.0	1065.8	1065.6
160°	1095.8	1094.5	1093.2	1091.9	1090.6	1090.4	1090.2	1089.9	1089.7	1089.6	1089.4
162.5°	1116.6	1115.1	1113.5	1112.0	1110.4	1110.2	1110.0	1109.7	1109.5	1109.4	1109.4
165°	1133.4	1131.9	1130.4	1128.8	1127.3	1127.3	1127.3	1127.3	1127.3	1127.3	1127.4
167.5°	1148.3	1146.8	1145.3	1143.7	1142.2	1142.2	1142.2	1142.2	1142.2	1142.2	1142.5
170°	1160.2	1158.7	1157.2	1155.6	1154.1	1154.3	1154.5	1154.8	1155.0	1155.1	1155.4
172.5°	1169.2	1167.7	1166.1	1164.6	1163.0	1163.2	1163.4	1163.7	1163.9	1164.0	1164.3
175°	1175.1	1173.6	1172.1	1170.5	1169.0	1169.4	1169.9	1170.3	1170.8	1171.0	1171.3
177.5°	1178.2	1176.9	1175.6	1174.2	1172.9	1173.3	1173.8	1174.2	1174.7	1174.9	1175.2
180°	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9

TEST NUMBER: P1010229

CATALOG NUMBER: S122RDIP-B675D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1483.1	1483.1	1483.1	1483.1
2.5°	1456.3	1453.2	1471.8	1492.4
5°	1426.4	1431.6	1455.3	1484.1
7.5°	1395.5	1406.8	1434.7	1472.8
10°	1352.2	1372.8	1415.1	1454.3
12.5°	1310.0	1337.8	1378.0	1424.4
15°	1262.6	1293.5	1342.9	1398.6
17.5°	1210.0	1245.0	1302.7	1363.6
20°	1154.3	1200.7	1261.5	1327.5
22.5°	1092.5	1148.1	1211.0	1284.2
25°	1032.7	1093.5	1156.4	1240.9
27.5°	974.0	1033.7	1103.8	1189.4
30°	915.2	969.8	1045.1	1136.8
32.5°	852.4	909.0	988.4	1082.2
35°	794.6	851.3	925.5	1018.3
37.5°	732.8	793.6	864.7	960.6
40°	660.6	731.8	800.8	892.5
42.5°	600.9	676.1	743.1	829.7
45°	553.5	624.6	680.2	764.7
47.5°	509.1	566.9	623.5	701.9
50°	466.9	511.2	570.0	640.0
52.5°	423.6	461.7	512.2	578.2
55°	384.4	420.5	465.9	516.4
57.5°	348.4	374.1	419.5	464.8
60°	308.2	335.0	370.0	408.1
62.5°	274.2	294.8	327.7	359.7
65°	238.1	257.7	282.4	312.3
67.5°	205.1	222.6	242.2	265.9
70°	175.2	188.6	203.0	223.7
72.5°	143.3	157.7	171.1	187.6
75°	117.5	123.7	135.0	146.4
77.5°	90.7	98.9	105.1	114.4
80°	64.9	72.1	74.2	81.4
82.5°	43.3	47.4	51.5	53.6
85°	24.7	26.8	30.9	32.0
87.5°	9.3	10.3	12.4	14.4
90°	8.9	6.3	3.6	1.0
92.5°	27.1	25.4	23.6	21.8
95°	58.2	56.0	53.8	51.6
97.5°	92.3	90.3	88.3	86.3
100°	131.3	129.6	127.8	126.0
102.5°	171.7	170.4	169.0	167.7
105°	215.3	214.7	214.0	213.4
107.5°	261.7	260.8	259.9	259.0
110°	306.6	305.3	304.0	302.7

TEST NUMBER: P1010229

CATALOG NUMBER: S122RDIP-B675D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	354.2	352.9	351.6	350.3
115°	400.9	399.6	398.2	396.9
117.5°	448.9	447.1	445.4	443.6
120°	495.5	493.8	492.0	490.2
122.5°	539.5	537.3	535.1	532.9
125°	583.5	581.5	579.5	577.5
127.5°	628.5	626.0	623.6	621.2
130°	670.5	667.6	664.8	661.9
132.5°	714.2	711.9	709.7	707.5
135°	754.5	752.0	749.6	747.2
137.5°	796.8	794.9	792.9	790.9
140°	835.5	833.6	831.6	829.6
142.5°	875.2	873.3	871.3	869.3
145°	911.6	910.1	908.5	907.0
147.5°	946.7	944.7	942.7	940.7
150°	979.4	978.1	976.8	975.5
152.5°	1010.2	1008.9	1007.5	1006.2
155°	1039.0	1038.3	1037.7	1037.0
157.5°	1065.1	1064.7	1064.2	1063.8
160°	1088.9	1088.5	1088.0	1087.6
162.5°	1109.4	1109.4	1109.4	1109.4
165°	1127.6	1127.9	1128.1	1128.3
167.5°	1143.2	1143.9	1144.5	1145.2
170°	1156.1	1156.8	1157.4	1158.1
172.5°	1165.0	1165.7	1166.3	1167.0
175°	1172.0	1172.6	1173.3	1173.9
177.5°	1175.9	1176.6	1177.2	1177.9
180°	1175.9	1175.9	1175.9	1175.9

(END OF REPORT)