

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010265

Luminaire Tested: S122RDIP-B865D1080UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010265
REPORT IS A COMBINATION OF REPORTS P988648 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B865D1080UB40-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7445.0 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010265

CATALOG NUMBER: S122RDIP-B865D1080UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1010265

CATALOG NUMBER: S122RDIP-B865D1080UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50
1	97	93	89	86	89	85	82	80	71	69	67	58	56	55	46	45	44
2	89	82	76	72	81	75	71	66	63	60	57	52	49	47	41	39	38
3	82	73	66	61	75	67	61	56	56	52	48	46	43	41	37	35	33
4	75	65	58	52	69	60	53	48	51	46	42	42	38	36	34	31	29
5	69	58	51	45	63	54	47	42	46	41	37	38	34	31	31	28	26
6	64	53	45	39	59	49	42	37	41	36	32	35	31	28	28	26	23
7	59	48	40	35	54	44	38	33	38	33	29	32	28	25	26	23	21
8	55	44	36	31	51	40	34	29	35	30	26	29	25	23	24	21	19
9	52	40	33	28	47	37	31	26	32	27	23	27	23	21	22	20	18
10	48	37	30	25	44	34	28	24	30	25	21	25	21	19	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	29870	29870	29870	29870
5°	29939	31728	30044	25346
10°	29610	33534	29820	20930
15°	28968	33545	29458	15724
20°	28195	27728	28808	12973
25°	27259	17326	27846	11036
30°	26061	11093	26769	9500
35°	24605	8525	25403	8130
40°	22984	7166	23965	7111
45°	21250	6099	22139	5971
50°	19473	5183	20384	5164
55°	17507	4504	18450	4445
60°	15758	3434	16592	3393
65°	14124	2584	14963	2932
70°	12325	2065	13291	2390
75°	10416	1581	11373	1807
80°	8271	1074	8902	1186
85°	5749	555	6300	586

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 27324 cd/sqm

TEST NUMBER: P1010265

CATALOG NUMBER: S122RDIP-B865D1080UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.0	2.4
10°-20°	499.6	6.7
20°-30°	643.0	8.6
30°-40°	610.0	8.2
40°-50°	522.8	7.0
50°-60°	398.1	5.3
60°-70°	251.1	3.4
70°-80°	125.3	1.7
80°-90°	36.1	0.5
90°-100°	234.0	3.1
100°-110°	824.0	11.1
110°-120°	865.4	11.6
120°-130°	712.0	9.6
130°-140°	572.0	7.7
140°-150°	432.0	5.8
150°-160°	303.7	4.1
160°-170°	178.8	2.4
170°-180°	58.2	0.8
0°-30°	1321.6	17.8
0°-40°	1931.6	25.9
0°-60°	2852.5	38.3
0°-90°	3264.9	43.9
90°-120°	1923.5	25.8
90°-150°	3639.5	48.9
90°-180°	4180.0	56.1
0°-180°	7445.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1887	1887	1887	1887	1887	
5°	1888	2100	1895	1677	1888	179
15°	1780	2370	1810	1111	1780	501
25°	1579	1264	1613	805	1579	725
35°	1296	623	1338	594	1296	811
45°	973	433	1014	424	973	751
55°	657	300	692	296	657	592
65°	397	156	421	177	397	394
75°	186	83	203	94	186	202
85°	41	24	45	25	41	46
90°	1	38	1	38	1	5
95°	40	132	40	132	40	42
105°	141	1301	141	1301	141	150
115°	248	1712	248	1712	248	246
125°	346	1389	346	1389	346	308
135°	406	1151	406	1151	406	314
145°	464	919	464	919	464	291
155°	528	772	528	772	528	243
165°	575	678	575	678	575	162
175°	599	611	599	611	599	57
180°	600	600	600	600	600	

TEST NUMBER: P1010265

CATALOG NUMBER: S122RDIP-B865D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0
2.5°	1898.8	1906.7	1910.6	1915.9	1927.7	1935.5	1947.3	1950.0	1948.7	1953.9	1939.5
5°	1888.3	1905.4	1921.1	1934.2	1955.2	1968.3	1982.7	1999.8	2003.7	2023.4	2011.6
7.5°	1873.9	1898.8	1921.1	1947.3	1978.8	1995.9	2018.2	2044.4	2056.2	2079.8	2086.3
10°	1850.3	1885.7	1923.7	1951.3	1994.5	2024.7	2045.7	2087.7	2115.2	2150.6	2145.4
12.5°	1812.3	1858.2	1909.3	1955.2	2011.6	2031.3	2070.6	2113.9	2149.3	2182.1	2210.9
15°	1779.5	1831.9	1888.3	1944.7	2009.0	2045.7	2085.0	2141.4	2179.4	2237.1	2262.1
17.5°	1734.9	1801.8	1868.7	1931.6	2007.7	2049.6	2098.1	2153.2	2209.6	2264.7	2284.4
20°	1689.0	1761.1	1833.3	1918.5	2005.0	2045.7	2095.5	2163.7	2218.8	2262.1	2262.1
22.5°	1633.9	1721.8	1804.4	1885.7	1980.1	2039.1	2090.3	2170.3	2209.6	2218.8	2183.4
25°	1578.9	1666.7	1757.2	1858.2	1965.7	2018.2	2075.9	2150.6	2163.7	2127.0	2035.2
27.5°	1513.3	1611.6	1713.9	1822.8	1935.5	2001.1	2053.6	2103.4	2078.5	1980.1	1837.2
30°	1446.4	1552.6	1668.0	1771.6	1908.0	1968.3	2012.9	2027.3	1948.7	1788.7	1603.8
32.5°	1376.9	1480.5	1602.5	1727.0	1864.7	1922.4	1951.3	1913.2	1769.0	1567.1	1341.5
35°	1295.6	1412.3	1539.5	1669.3	1805.7	1849.0	1866.0	1772.9	1588.0	1327.1	1102.8
37.5°	1222.2	1338.9	1475.3	1607.7	1740.1	1763.8	1746.7	1601.1	1366.4	1108.1	889.1
40°	1135.6	1260.2	1394.0	1542.1	1651.0	1657.5	1615.6	1426.7	1135.6	893.0	758.0
42.5°	1055.6	1181.5	1315.3	1466.1	1548.7	1526.4	1470.0	1222.2	948.1	769.8	660.9
45°	973.0	1092.3	1236.6	1370.3	1429.4	1376.9	1291.7	1028.1	796.0	662.2	578.3
47.5°	893.0	1004.5	1147.4	1275.9	1286.4	1227.4	1126.4	861.5	689.8	582.2	514.0
50°	814.3	925.8	1059.6	1165.8	1155.3	1074.0	959.9	748.8	599.3	514.0	457.7
52.5°	735.7	836.6	966.5	1050.4	1005.8	927.1	814.3	634.7	523.2	448.5	405.2
55°	657.0	751.4	862.9	932.4	861.5	771.1	691.1	544.2	453.7	393.4	360.6
57.5°	591.4	666.2	768.4	810.4	725.2	654.4	584.9	468.1	393.4	350.1	312.1
60°	519.3	587.5	671.4	696.3	608.5	550.8	491.8	396.0	337.0	299.0	274.1
62.5°	457.7	514.0	578.3	578.3	500.9	457.7	413.1	331.8	283.2	253.1	241.3
65°	397.3	438.0	483.9	478.6	413.1	375.0	339.6	274.1	237.4	216.4	204.6
67.5°	338.3	369.8	400.0	381.6	334.4	301.6	268.8	221.6	196.7	182.3	166.5
70°	284.6	309.5	325.2	308.2	261.0	233.4	209.8	178.3	158.7	140.3	131.1
72.5°	238.7	249.2	254.4	233.4	194.1	178.3	161.3	139.0	122.0	112.8	110.2
75°	186.2	195.4	191.5	175.7	142.9	131.1	118.0	102.3	98.4	93.1	90.5
77.5°	145.6	145.6	139.0	124.6	102.3	93.1	87.9	80.0	76.1	74.7	72.1
80°	103.6	102.3	98.4	82.6	69.5	64.3	64.3	59.0	57.7	55.1	55.1
82.5°	68.2	68.2	62.9	49.8	45.9	44.6	43.3	40.7	40.7	39.3	39.3
85°	40.7	38.0	31.5	27.5	26.2	26.2	24.9	23.6	24.9	23.6	23.6
87.5°	18.4	14.4	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5
90°	1.2	4.6	9.2	11.5	13.9	15.6	17.3	23.1	31.2	38.1	39.2
92.5°	17.3	24.2	33.5	39.2	48.5	54.8	61.2	92.3	136.2	175.5	177.8
95°	40.4	45.0	56.6	67.0	85.4	99.2	113.1	166.2	266.6	400.6	452.5
97.5°	60.0	67.0	79.6	94.7	115.4	131.0	146.6	214.7	354.4	570.2	737.6
100°	88.9	92.3	102.7	121.2	144.3	160.4	176.6	237.8	378.6	628.0	911.9
102.5°	115.4	117.7	128.1	146.6	170.8	187.0	203.2	258.6	379.8	606.0	917.7
105°	140.8	145.4	153.5	170.8	196.2	212.4	228.6	282.8	385.5	576.0	855.4
107.5°	168.5	172.0	180.1	196.2	221.6	237.8	254.0	307.0	398.2	559.8	797.6
110°	196.2	200.9	207.8	222.8	247.0	263.8	280.5	331.3	414.4	555.2	758.4

TEST NUMBER: P1010265

CATALOG NUMBER: S122RDIP-B865D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	221.6	226.2	234.3	248.2	271.3	288.6	305.9	354.4	431.7	556.4	733.0
115°	248.2	254.0	260.9	274.7	297.8	313.4	329.0	378.6	449.0	561.0	715.7
117.5°	275.9	280.5	287.4	300.1	322.1	338.2	354.4	400.6	467.5	567.9	706.4
120°	301.3	305.9	312.8	323.2	346.3	362.5	378.6	423.6	486.0	574.9	698.4
122.5°	325.5	329.0	335.9	347.5	370.5	387.2	404.0	445.6	502.1	582.9	693.7
125°	346.3	349.8	356.7	370.5	393.6	409.8	425.9	467.5	519.4	591.0	688.0
127.5°	363.6	368.2	377.5	392.5	414.4	431.2	447.9	488.3	535.6	599.1	684.5
130°	378.6	383.2	394.8	410.9	434.0	450.2	466.3	506.7	550.6	608.3	682.2
132.5°	392.5	398.2	410.9	428.3	452.5	468.6	484.8	522.9	565.6	617.6	681.1
135°	406.3	410.9	424.8	442.1	468.7	484.8	501.0	537.9	578.3	624.5	679.9
137.5°	419.0	424.8	438.6	457.1	483.7	498.7	513.7	550.6	588.7	631.4	679.9
140°	434.0	438.6	452.5	471.0	496.4	511.4	526.4	561.0	596.8	636.0	678.7
142.5°	449.0	452.5	465.2	483.7	507.9	521.8	535.6	569.1	603.7	639.5	678.7
145°	464.0	468.7	480.2	497.5	520.6	533.3	546.0	577.2	609.5	641.8	676.4
147.5°	480.2	483.7	495.2	511.4	531.0	542.6	554.1	584.1	612.9	643.0	673.0
150°	496.4	499.8	509.1	524.1	541.4	551.8	562.2	588.7	615.3	641.8	669.5
152.5°	512.5	513.7	522.9	535.6	551.8	561.0	570.2	593.3	616.4	639.5	663.7
155°	527.5	528.7	535.6	548.3	561.0	569.6	578.3	597.9	617.6	637.2	656.8
157.5°	540.2	541.4	547.1	558.7	569.1	576.6	584.1	601.4	617.6	632.6	649.9
160°	552.9	554.1	558.7	567.9	577.2	583.6	589.9	603.7	617.6	629.1	643.0
162.5°	565.6	564.5	569.1	576.0	584.1	588.7	593.3	604.9	616.4	625.6	637.2
165°	574.9	573.7	576.0	582.9	588.7	592.2	595.6	606.0	614.1	621.0	629.1
167.5°	582.9	581.8	584.1	588.7	593.3	595.6	597.9	606.0	612.9	616.4	622.2
170°	591.0	588.7	589.9	593.3	595.6	597.4	599.1	604.9	610.6	612.9	616.4
172.5°	595.6	594.5	593.3	596.8	597.9	599.0	600.2	603.7	607.2	608.3	609.5
175°	599.1	597.9	596.8	599.1	599.1	599.7	600.2	602.6	604.9	603.7	604.9
177.5°	601.4	599.1	597.9	600.2	600.2	600.2	600.2	601.4	603.7	601.4	600.2
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P1010265

CATALOG NUMBER: S122RDIP-B865D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0
2.5°	1953.9	1956.5	1960.5	1978.8	1981.4	1986.7	1984.1	1984.1	1985.4	1982.7	1984.1
5°	2037.8	2041.8	2061.4	2083.7	2089.0	2083.7	2090.3	2099.5	2099.5	2099.5	2096.8
7.5°	2116.5	2130.9	2153.2	2186.0	2192.6	2199.1	2210.9	2203.1	2205.7	2217.5	2213.5
10°	2192.6	2213.5	2238.5	2266.0	2280.4	2289.6	2294.8	2306.6	2334.2	2302.7	2314.5
12.5°	2264.7	2294.8	2321.1	2351.2	2361.7	2373.5	2377.5	2387.9	2387.9	2386.6	2395.8
15°	2311.9	2339.4	2363.0	2382.7	2385.3	2382.7	2380.1	2381.4	2385.3	2369.6	2378.8
17.5°	2322.4	2325.0	2332.9	2325.0	2326.3	2298.8	2283.0	2279.1	2242.4	2243.7	2273.9
20°	2271.2	2226.7	2214.9	2171.6	2145.4	2074.5	2071.9	2052.2	1974.9	1998.5	1993.2
22.5°	2130.9	2054.9	1953.9	1904.1	1879.1	1804.4	1746.7	1706.1	1678.5	1651.0	1639.2
25°	1946.0	1822.8	1679.8	1581.5	1567.1	1497.5	1391.3	1341.5	1282.5	1264.1	1295.6
27.5°	1707.4	1547.4	1386.1	1235.3	1207.7	1144.8	1091.0	1055.6	987.4	983.5	986.1
30°	1383.5	1222.2	1087.1	988.7	920.6	891.7	856.3	830.1	802.5	813.0	815.7
32.5°	1136.9	983.5	857.6	805.2	773.7	755.3	725.2	708.1	696.3	692.4	691.1
35°	903.5	801.2	744.8	693.7	675.3	662.2	639.9	632.1	621.6	622.9	622.9
37.5°	773.7	688.5	646.5	620.3	603.2	596.7	582.2	574.4	567.8	565.2	569.1
40°	667.5	608.5	582.2	558.6	544.2	541.6	533.7	524.5	516.7	518.0	521.9
42.5°	590.1	556.0	524.5	506.2	495.7	491.8	485.2	478.6	478.6	474.7	473.4
45°	528.5	500.9	474.7	457.7	451.1	445.9	438.0	436.7	431.4	432.7	434.1
47.5°	473.4	451.1	431.4	414.4	407.8	406.5	398.6	393.4	393.4	392.1	390.8
50°	423.6	401.3	384.2	375.0	365.9	363.2	361.9	360.6	358.0	358.0	359.3
52.5°	382.9	360.6	347.5	339.6	334.4	331.8	331.8	330.5	330.5	330.5	329.1
55°	338.3	320.0	309.5	306.9	304.2	302.9	301.6	299.0	297.7	300.3	297.7
57.5°	296.4	289.8	280.6	278.0	271.4	271.4	267.5	264.9	262.3	264.9	264.9
60°	263.6	254.4	249.2	241.3	236.0	230.8	224.2	222.9	220.3	219.0	217.7
62.5°	229.5	221.6	208.5	196.7	188.8	183.6	181.0	179.7	179.7	178.3	178.3
65°	191.5	173.1	166.5	162.6	161.3	160.0	157.4	156.0	157.4	156.0	157.4
67.5°	149.5	146.9	142.9	140.3	139.0	137.7	137.7	136.4	136.4	136.4	136.4
70°	129.8	123.3	122.0	119.3	119.3	118.0	118.0	118.0	118.0	116.7	119.3
72.5°	107.5	103.6	102.3	101.0	101.0	101.0	99.7	99.7	99.7	98.4	99.7
75°	87.9	86.5	83.9	83.9	82.6	83.9	82.6	82.6	81.3	82.6	82.6
77.5°	70.8	69.5	68.2	68.2	66.9	66.9	66.9	66.9	66.9	66.9	68.2
80°	53.8	52.5	51.1	52.5	51.1	52.5	51.1	51.1	52.5	51.1	51.1
82.5°	39.3	38.0	38.0	36.7	36.7	36.7	36.7	36.7	36.7	36.7	36.7
85°	23.6	22.3	22.3	23.6	22.3	23.6	22.3	22.3	22.3	23.6	23.6
87.5°	10.5	11.8	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	11.8
90°	38.1	36.9	34.6	36.9	37.5	38.1	38.1	38.1	38.1	38.1	38.1
92.5°	148.9	116.6	99.3	86.6	81.9	77.3	76.2	71.6	72.7	70.4	72.7
95°	395.9	302.4	232.0	183.5	170.8	158.1	143.1	133.9	130.4	131.6	130.4
97.5°	743.4	618.7	494.1	377.5	342.8	308.2	263.2	240.1	227.4	220.5	227.4
100°	1078.1	1053.9	910.8	752.6	682.8	612.9	517.1	467.5	434.0	413.2	434.0
102.5°	1202.8	1339.0	1334.4	1229.4	1154.4	1079.3	973.1	879.6	835.7	805.7	835.7
105°	1162.4	1402.5	1532.9	1547.9	1528.9	1509.9	1438.3	1366.7	1317.1	1300.9	1317.1
107.5°	1077.0	1334.4	1528.3	1641.4	1664.5	1687.6	1686.5	1676.1	1661.1	1634.5	1661.1
110°	997.3	1240.9	1447.5	1595.3	1642.6	1689.9	1739.6	1761.5	1771.9	1770.7	1771.9

TEST NUMBER: P1010265

CATALOG NUMBER: S122RDIP-B865D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	941.9	1155.5	1351.7	1512.2	1568.2	1624.1	1698.0	1738.4	1760.3	1768.4	1760.3
115°	898.1	1088.5	1266.3	1417.5	1477.0	1536.4	1618.4	1671.5	1701.5	1711.9	1701.5
117.5°	868.1	1033.1	1192.4	1333.2	1389.8	1446.4	1530.6	1587.2	1618.4	1626.4	1618.4
120°	845.0	993.9	1137.0	1259.4	1311.9	1364.4	1445.2	1499.5	1532.9	1544.5	1532.9
122.5°	825.3	962.7	1090.8	1205.1	1251.3	1297.5	1367.9	1421.0	1449.8	1459.1	1449.8
125°	806.9	932.7	1051.6	1153.2	1196.4	1239.7	1306.7	1350.6	1379.4	1388.7	1379.4
127.5°	789.6	902.7	1012.3	1109.3	1149.7	1190.1	1249.0	1290.5	1315.9	1322.9	1315.9
130°	772.2	873.8	973.1	1064.3	1102.4	1140.5	1197.0	1236.3	1259.4	1268.6	1259.4
132.5°	758.4	846.1	936.2	1018.1	1053.3	1088.5	1143.9	1183.2	1204.0	1212.0	1204.0
135°	745.7	820.7	896.9	973.1	1005.4	1037.7	1087.4	1125.5	1146.2	1150.9	1146.2
137.5°	736.5	799.9	865.7	928.1	957.0	985.8	1033.1	1066.6	1085.1	1092.0	1085.1
140°	728.4	780.3	835.7	888.8	914.2	939.6	976.6	1006.6	1023.9	1030.8	1023.9
142.5°	720.3	764.2	809.2	853.0	873.2	893.4	928.1	954.6	969.6	969.6	969.6
145°	713.4	749.2	787.2	823.0	839.8	856.5	884.2	903.8	915.4	918.8	915.4
147.5°	706.4	737.6	768.8	797.6	810.3	823.0	847.3	863.4	871.5	873.8	871.5
150°	697.2	724.9	750.3	774.6	785.0	795.3	812.6	826.5	833.4	834.6	833.4
152.5°	689.1	712.2	735.3	754.9	763.6	772.2	784.9	796.5	801.1	801.1	801.1
155°	678.7	700.7	719.1	736.5	742.8	749.2	761.9	769.9	774.6	772.2	774.6
157.5°	669.5	686.8	703.0	718.0	723.2	728.4	737.6	744.5	746.8	746.8	746.8
160°	659.1	674.1	686.8	699.5	703.6	707.6	715.7	721.5	722.6	722.6	722.6
162.5°	649.9	661.4	671.8	682.2	685.1	688.0	696.1	699.5	700.7	699.5	700.7
165°	639.5	648.7	656.8	664.9	667.2	669.5	674.1	678.7	678.7	677.6	678.7
167.5°	629.1	636.0	643.0	648.7	651.0	653.3	655.7	658.0	658.0	656.8	658.0
170°	621.0	626.8	630.3	634.9	636.0	637.2	638.3	641.8	640.6	638.3	640.6
172.5°	612.9	616.4	618.7	622.2	622.8	623.3	624.5	625.6	624.5	623.3	624.5
175°	606.0	609.5	610.6	611.8	612.3	612.9	612.9	614.1	612.9	610.6	612.9
177.5°	601.4	603.7	603.7	604.9	604.9	604.9	604.9	604.9	603.7	601.4	603.7
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P1010265

CATALOG NUMBER: S122RDIP-B865D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0
2.5°	1989.3	1980.1	1977.5	1980.1	1977.5	1978.8	1969.6	1935.5	1944.7	1930.3	1938.2
5°	2102.1	2094.2	2077.2	2074.5	2071.9	2069.3	2056.2	2026.0	2014.2	1994.5	1993.2
7.5°	2209.6	2209.6	2196.5	2187.3	2175.5	2166.3	2149.3	2104.7	2086.3	2062.7	2049.6
10°	2315.8	2281.7	2296.2	2287.0	2258.1	2252.9	2221.4	2195.2	2159.8	2136.2	2115.2
12.5°	2391.9	2381.4	2368.3	2360.4	2352.5	2335.5	2314.5	2247.6	2229.3	2182.1	2158.5
15°	2389.3	2382.7	2386.6	2386.6	2384.0	2380.1	2363.0	2314.5	2283.0	2237.1	2196.5
17.5°	2260.7	2277.8	2294.8	2306.6	2332.9	2344.7	2360.4	2331.6	2311.9	2272.6	2229.3
20°	2036.5	2078.5	2128.3	2138.8	2162.4	2231.9	2263.4	2288.3	2296.2	2283.0	2247.6
22.5°	1724.4	1759.8	1880.5	1877.8	1911.9	1994.5	2086.3	2161.1	2220.1	2252.9	2239.8
25°	1350.7	1400.5	1464.8	1513.3	1624.7	1748.0	1862.1	1981.4	2083.7	2174.2	2196.5
27.5°	1021.5	1087.1	1138.2	1202.5	1258.9	1404.4	1551.3	1737.5	1856.9	2028.6	2117.8
30°	826.1	856.3	907.4	937.6	965.1	1076.6	1243.1	1426.7	1636.6	1834.6	1988.0
32.5°	705.5	726.5	764.5	777.6	806.5	881.2	986.1	1154.0	1370.3	1610.3	1812.3
35°	633.4	655.7	663.5	675.3	698.9	746.2	818.3	940.2	1135.6	1370.3	1611.6
37.5°	571.7	583.5	605.8	613.7	621.6	657.0	705.5	790.7	920.6	1113.3	1380.8
40°	528.5	535.0	546.8	553.4	558.6	583.5	626.8	684.5	780.2	927.1	1173.6
42.5°	482.6	490.4	498.3	506.2	512.7	532.4	558.6	613.7	678.0	789.4	967.8
45°	438.0	443.2	452.4	457.7	466.8	482.6	506.2	544.2	601.9	672.7	817.0
47.5°	397.3	403.9	407.8	414.4	420.9	438.0	460.3	485.2	532.4	601.9	706.8
50°	360.6	368.5	373.7	375.0	380.3	396.0	414.4	441.9	472.1	525.8	617.6
52.5°	334.4	335.7	339.6	344.9	343.6	352.8	369.8	390.8	422.3	465.5	532.4
55°	304.2	308.2	310.8	312.1	312.1	320.0	329.1	348.8	373.7	409.1	465.5
57.5°	266.2	270.1	278.0	280.6	284.6	288.5	292.4	305.5	326.5	360.6	406.5
60°	226.9	229.5	237.4	242.6	245.2	255.7	261.0	271.4	283.2	308.2	351.4
62.5°	182.3	184.9	188.8	194.1	199.3	215.1	228.2	238.7	247.8	264.9	300.3
65°	158.7	160.0	162.6	163.9	165.2	171.8	183.6	198.0	215.1	228.2	249.2
67.5°	137.7	139.0	140.3	142.9	144.2	145.6	150.8	154.7	171.8	190.1	205.9
70°	118.0	120.6	122.0	122.0	123.3	125.9	128.5	133.8	139.0	148.2	167.9
72.5°	99.7	101.0	103.6	103.6	103.6	106.2	108.8	111.5	114.1	119.3	127.2
75°	82.6	85.2	85.2	85.2	86.5	86.5	89.2	91.8	94.4	98.4	101.0
77.5°	68.2	68.2	68.2	68.2	69.5	69.5	70.8	73.4	74.7	76.1	78.7
80°	51.1	52.5	52.5	52.5	53.8	53.8	53.8	56.4	57.7	57.7	60.3
82.5°	38.0	38.0	38.0	39.3	38.0	39.3	39.3	40.7	39.3	40.7	42.0
85°	23.6	23.6	23.6	24.9	24.9	24.9	24.9	24.9	24.9	24.9	26.2
87.5°	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	13.1	11.8	11.8
90°	38.1	38.1	38.1	37.5	36.9	34.6	36.9	38.1	39.2	38.1	31.2
92.5°	71.6	76.2	77.3	81.9	86.6	99.3	116.6	148.9	177.8	175.5	136.2
95°	133.9	143.1	158.1	170.8	183.5	232.0	302.4	395.9	452.5	400.6	266.6
97.5°	240.1	263.2	308.2	342.8	377.5	494.1	618.7	743.4	737.6	570.2	354.4
100°	467.5	517.1	612.9	682.8	752.6	910.8	1053.9	1078.1	911.9	628.0	378.6
102.5°	879.6	973.1	1079.3	1154.4	1229.4	1334.4	1339.0	1202.8	917.7	606.0	379.8
105°	1366.7	1438.3	1509.9	1528.9	1547.9	1532.9	1402.5	1162.4	855.4	576.0	385.5
107.5°	1676.1	1686.5	1687.6	1664.5	1641.4	1528.3	1334.4	1077.0	797.6	559.8	398.2
110°	1761.5	1739.6	1689.9	1642.6	1595.3	1447.5	1240.9	997.3	758.4	555.2	414.4

TEST NUMBER: P1010265

CATALOG NUMBER: S122RDIP-B865D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1738.4	1698.0	1624.1	1568.2	1512.2	1351.7	1155.5	941.9	733.0	556.4	431.7
115°	1671.5	1618.4	1536.4	1477.0	1417.5	1266.3	1088.5	898.1	715.7	561.0	449.0
117.5°	1587.2	1530.6	1446.4	1389.8	1333.2	1192.4	1033.1	868.1	706.4	567.9	467.5
120°	1499.5	1445.2	1364.4	1311.9	1259.4	1137.0	993.9	845.0	698.4	574.9	486.0
122.5°	1421.0	1367.9	1297.5	1251.3	1205.1	1090.8	962.7	825.3	693.7	582.9	502.1
125°	1350.6	1306.7	1239.7	1196.4	1153.2	1051.6	932.7	806.9	688.0	591.0	519.4
127.5°	1290.5	1249.0	1190.1	1149.7	1109.3	1012.3	902.7	789.6	684.5	599.1	535.6
130°	1236.3	1197.0	1140.5	1102.4	1064.3	973.1	873.8	772.2	682.2	608.3	550.6
132.5°	1183.2	1143.9	1088.5	1053.3	1018.1	936.2	846.1	758.4	681.1	617.6	565.6
135°	1125.5	1087.4	1037.7	1005.4	973.1	896.9	820.7	745.7	679.9	624.5	578.3
137.5°	1066.6	1033.1	985.8	957.0	928.1	865.7	799.9	736.5	679.9	631.4	588.7
140°	1006.6	976.6	939.6	914.2	888.8	835.7	780.3	728.4	678.7	636.0	596.8
142.5°	954.6	928.1	893.4	873.2	853.0	809.2	764.2	720.3	678.7	639.5	603.7
145°	903.8	884.2	856.5	839.8	823.0	787.2	749.2	713.4	676.4	641.8	609.5
147.5°	863.4	847.3	823.0	810.3	797.6	768.8	737.6	706.4	673.0	643.0	612.9
150°	826.5	812.6	795.3	785.0	774.6	750.3	724.9	697.2	669.5	641.8	615.3
152.5°	796.5	784.9	772.2	763.6	754.9	735.3	712.2	689.1	663.7	639.5	616.4
155°	769.9	761.9	749.2	742.8	736.5	719.1	700.7	678.7	656.8	637.2	617.6
157.5°	744.5	737.6	728.4	723.2	718.0	703.0	686.8	669.5	649.9	632.6	617.6
160°	721.5	715.7	707.6	703.6	699.5	686.8	674.1	659.1	643.0	629.1	617.6
162.5°	699.5	696.1	688.0	685.1	682.2	671.8	661.4	649.9	637.2	625.6	616.4
165°	678.7	674.1	669.5	667.2	664.9	656.8	648.7	639.5	629.1	621.0	614.1
167.5°	658.0	655.7	653.3	651.0	648.7	643.0	636.0	629.1	622.2	616.4	612.9
170°	641.8	638.3	637.2	636.0	634.9	630.3	626.8	621.0	616.4	612.9	610.6
172.5°	625.6	624.5	623.3	622.8	622.2	618.7	616.4	612.9	609.5	608.3	607.2
175°	614.1	612.9	612.9	612.3	611.8	610.6	609.5	606.0	604.9	603.7	604.9
177.5°	604.9	604.9	604.9	604.9	604.9	603.7	603.7	601.4	600.2	601.4	603.7
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P1010265

CATALOG NUMBER: S122RDIP-B865D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0
2.5°	1926.4	1919.8	1919.8	1915.9	1915.9	1894.9	1894.9	1901.4	1893.6	1884.4	1871.3
5°	1976.2	1961.8	1957.8	1952.6	1935.5	1909.3	1898.8	1894.9	1879.1	1859.5	1837.2
7.5°	2023.4	1999.8	1988.0	1976.2	1953.9	1917.2	1896.2	1881.8	1858.2	1828.0	1799.2
10°	2069.3	2039.1	2009.0	1994.5	1963.1	1917.2	1887.0	1863.4	1829.3	1788.7	1748.0
12.5°	2111.3	2048.3	2043.1	2014.2	1968.3	1915.9	1870.0	1835.9	1792.6	1745.4	1698.2
15°	2148.0	2083.7	2052.2	2026.0	1965.7	1900.1	1851.6	1809.6	1751.9	1698.2	1640.5
17.5°	2166.3	2096.8	2075.9	2032.6	1970.9	1885.7	1820.1	1769.0	1706.1	1641.8	1576.2
20°	2184.7	2103.4	2069.3	2039.1	1955.2	1858.2	1784.7	1725.7	1656.2	1580.2	1508.0
22.5°	2193.9	2103.4	2062.7	2020.8	1939.5	1828.0	1741.5	1672.0	1590.7	1513.3	1426.7
25°	2178.1	2095.5	2047.0	2003.7	1911.9	1791.3	1691.6	1612.9	1526.4	1438.5	1350.7
27.5°	2138.8	2077.2	2020.8	1976.2	1873.9	1744.1	1639.2	1550.0	1460.8	1362.5	1273.3
30°	2065.4	2037.8	1993.2	1943.4	1831.9	1702.1	1577.5	1485.7	1387.4	1289.0	1195.9
32.5°	1951.3	1974.9	1946.0	1902.8	1782.1	1644.4	1512.0	1418.9	1311.3	1205.1	1119.9
35°	1812.3	1896.2	1880.5	1850.3	1729.7	1582.8	1450.3	1337.6	1230.0	1122.5	1037.3
37.5°	1660.2	1787.4	1800.5	1782.1	1669.3	1519.8	1374.3	1264.1	1154.0	1045.1	958.6
40°	1451.7	1647.0	1689.0	1696.9	1606.4	1443.8	1291.7	1184.1	1075.3	969.1	864.2
42.5°	1260.2	1506.7	1559.2	1592.0	1526.4	1369.0	1215.6	1096.3	988.7	893.0	788.1
45°	1080.5	1337.6	1422.8	1464.8	1435.9	1283.8	1125.1	1013.7	915.3	827.5	726.5
47.5°	895.6	1154.0	1273.3	1340.2	1340.2	1197.3	1038.6	928.4	834.0	759.3	670.1
50°	772.4	987.4	1110.7	1198.6	1222.2	1109.4	959.9	852.4	763.2	681.9	613.7
52.5°	658.3	851.1	953.3	1045.1	1113.3	1015.0	872.0	775.0	687.1	611.1	557.3
55°	569.1	713.4	806.5	907.4	983.5	919.2	786.8	692.4	616.3	553.4	507.5
57.5°	483.9	609.8	685.8	775.0	856.3	807.8	701.6	620.3	553.4	498.3	457.7
60°	411.8	514.0	573.1	642.6	743.5	709.4	621.6	546.8	493.1	443.2	409.1
62.5°	350.1	431.4	481.3	531.1	622.9	607.2	539.0	481.3	435.4	393.4	364.6
65°	287.2	354.1	393.4	436.7	510.1	516.7	461.6	420.9	379.0	342.3	316.0
67.5°	232.1	284.6	320.0	356.7	415.7	434.1	396.0	361.9	326.5	296.4	272.8
70°	187.5	224.2	250.5	279.3	327.8	350.1	330.5	306.9	278.0	253.1	232.1
72.5°	148.2	171.8	187.5	209.8	249.2	271.4	270.1	249.2	228.2	211.1	194.1
75°	108.8	127.2	140.3	154.7	186.2	207.2	212.4	203.3	182.3	169.2	156.0
77.5°	82.6	93.1	99.7	110.2	132.4	150.8	158.7	156.0	141.6	131.1	122.0
80°	62.9	65.6	68.2	72.1	90.5	107.5	112.8	111.5	103.6	99.7	89.2
82.5°	44.6	45.9	47.2	48.5	55.1	69.5	74.7	77.4	70.8	66.9	57.7
85°	26.2	27.5	27.5	30.2	31.5	35.4	44.6	44.6	43.3	38.0	36.7
87.5°	13.1	13.1	11.8	11.8	13.1	14.4	17.0	19.7	17.0	15.7	14.4
90°	23.1	17.3	15.6	13.9	11.5	9.2	4.6	1.2	4.6	9.2	11.5
92.5°	92.3	61.2	54.8	48.5	39.2	33.5	24.2	17.3	24.2	33.5	39.2
95°	166.2	113.1	99.2	85.4	67.0	56.6	45.0	40.4	45.0	56.6	67.0
97.5°	214.7	146.6	131.0	115.4	94.7	79.6	67.0	60.0	67.0	79.6	94.7
100°	237.8	176.6	160.4	144.3	121.2	102.7	92.3	88.9	92.3	102.7	121.2
102.5°	258.6	203.2	187.0	170.8	146.6	128.1	117.7	115.4	117.7	128.1	146.6
105°	282.8	228.6	212.4	196.2	170.8	153.5	145.4	140.8	145.4	153.5	170.8
107.5°	307.0	254.0	237.8	221.6	196.2	180.1	172.0	168.5	172.0	180.1	196.2
110°	331.3	280.5	263.8	247.0	222.8	207.8	200.9	196.2	200.9	207.8	222.8

TEST NUMBER: P1010265

CATALOG NUMBER: S122RDIP-B865D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	354.4	305.9	288.6	271.3	248.2	234.3	226.2	221.6	226.2	234.3	248.2
115°	378.6	329.0	313.4	297.8	274.7	260.9	254.0	248.2	254.0	260.9	274.7
117.5°	400.6	354.4	338.2	322.1	300.1	287.4	280.5	275.9	280.5	287.4	300.1
120°	423.6	378.6	362.5	346.3	323.2	312.8	305.9	301.3	305.9	312.8	323.2
122.5°	445.6	404.0	387.2	370.5	347.5	335.9	329.0	325.5	329.0	335.9	347.5
125°	467.5	425.9	409.8	393.6	370.5	356.7	349.8	346.3	349.8	356.7	370.5
127.5°	488.3	447.9	431.2	414.4	392.5	377.5	368.2	363.6	368.2	377.5	392.5
130°	506.7	466.3	450.2	434.0	410.9	394.8	383.2	378.6	383.2	394.8	410.9
132.5°	522.9	484.8	468.6	452.5	428.3	410.9	398.2	392.5	398.2	410.9	428.3
135°	537.9	501.0	484.8	468.7	442.1	424.8	410.9	406.3	410.9	424.8	442.1
137.5°	550.6	513.7	498.7	483.7	457.1	438.6	424.8	419.0	424.8	438.6	457.1
140°	561.0	526.4	511.4	496.4	471.0	452.5	438.6	434.0	438.6	452.5	471.0
142.5°	569.1	535.6	521.8	507.9	483.7	465.2	452.5	449.0	452.5	465.2	483.7
145°	577.2	546.0	533.3	520.6	497.5	480.2	468.7	464.0	468.7	480.2	497.5
147.5°	584.1	554.1	542.6	531.0	511.4	495.2	483.7	480.2	483.7	495.2	511.4
150°	588.7	562.2	551.8	541.4	524.1	509.1	499.8	496.4	499.8	509.1	524.1
152.5°	593.3	570.2	561.0	551.8	535.6	522.9	513.7	512.5	513.7	522.9	535.6
155°	597.9	578.3	569.6	561.0	548.3	535.6	528.7	527.5	528.7	535.6	548.3
157.5°	601.4	584.1	576.6	569.1	558.7	547.1	541.4	540.2	541.4	547.1	558.7
160°	603.7	589.9	583.6	577.2	567.9	558.7	554.1	552.9	554.1	558.7	567.9
162.5°	604.9	593.3	588.7	584.1	576.0	569.1	564.5	565.6	564.5	569.1	576.0
165°	606.0	595.6	592.2	588.7	582.9	576.0	573.7	574.9	573.7	576.0	582.9
167.5°	606.0	597.9	595.6	593.3	588.7	584.1	581.8	582.9	581.8	584.1	588.7
170°	604.9	599.1	597.4	595.6	593.3	589.9	588.7	591.0	588.7	589.9	593.3
172.5°	603.7	600.2	599.0	597.9	596.8	593.3	594.5	595.6	594.5	593.3	596.8
175°	602.6	600.2	599.7	599.1	599.1	596.8	597.9	599.1	597.9	596.8	599.1
177.5°	601.4	600.2	600.2	600.2	600.2	597.9	599.1	601.4	599.1	597.9	600.2
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P1010265

CATALOG NUMBER: S122RDIP-B865D1080UB40-4FO-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0
2.5°	1866.0	1867.3	1871.3	1859.5	1841.1	1833.3	1809.6	1805.7	1801.8	1801.8	1805.7
5°	1824.1	1818.8	1820.1	1797.8	1771.6	1755.9	1723.1	1728.3	1711.3	1700.8	1703.4
7.5°	1778.2	1763.8	1762.4	1733.6	1700.8	1672.0	1637.9	1630.0	1614.3	1595.9	1588.0
10°	1720.5	1710.0	1690.3	1657.5	1615.6	1592.0	1546.1	1518.5	1514.6	1487.1	1476.6
12.5°	1661.5	1643.1	1623.4	1577.5	1530.3	1492.3	1458.2	1428.0	1407.1	1383.5	1367.7
15°	1593.3	1571.0	1548.7	1500.2	1445.1	1407.1	1355.9	1311.3	1249.7	1201.2	1173.6
17.5°	1518.5	1493.6	1463.5	1409.7	1355.9	1303.5	1209.1	1156.6	1113.3	1084.5	1067.4
20°	1441.2	1413.6	1383.5	1329.7	1236.6	1144.8	1092.3	1051.7	1025.5	996.6	975.6
22.5°	1359.9	1331.0	1298.2	1214.3	1115.9	1051.7	1011.0	973.0	935.0	919.2	908.8
25°	1283.8	1257.6	1215.6	1101.5	1024.2	965.1	919.2	894.3	874.7	853.7	834.0
27.5°	1205.1	1156.6	1097.6	1001.9	953.3	893.0	860.2	841.9	807.8	793.4	784.2
30°	1110.7	1056.9	1000.6	932.4	876.0	834.0	803.9	773.7	754.0	739.6	723.9
32.5°	1015.0	963.8	928.4	857.6	815.7	772.4	743.5	725.2	696.3	687.1	680.6
35°	932.4	889.1	857.6	799.9	760.6	721.2	700.3	672.7	654.4	637.3	626.8
37.5°	851.1	827.5	794.7	746.2	704.2	672.7	643.9	634.7	609.8	600.6	590.1
40°	794.7	759.3	731.7	689.8	654.4	620.3	601.9	580.9	563.9	549.5	545.5
42.5°	726.5	700.3	684.5	638.6	601.9	582.2	559.9	536.3	523.2	511.4	497.0
45°	675.3	651.7	629.4	592.7	559.9	535.0	515.4	499.6	477.3	472.1	449.8
47.5°	621.6	598.0	580.9	544.2	514.0	490.4	476.0	455.0	436.7	424.9	414.4
50°	567.8	548.1	532.4	500.9	474.7	449.8	430.1	409.1	401.3	381.6	375.0
52.5°	516.7	503.6	486.5	456.3	430.1	409.1	388.2	371.1	359.3	348.8	340.9
55°	473.4	452.4	444.5	411.8	389.5	367.2	348.8	338.3	323.9	317.3	310.8
57.5°	424.9	413.1	400.0	375.0	350.1	329.1	316.0	300.3	292.4	284.6	279.3
60°	382.9	365.9	355.4	334.4	312.1	292.4	280.6	268.8	258.3	251.8	241.3
62.5°	334.4	321.3	314.7	292.4	274.1	255.7	245.2	233.4	225.6	213.7	200.6
65°	292.4	281.9	274.1	255.7	238.7	221.6	211.1	196.7	186.2	179.7	178.3
67.5°	255.7	247.8	236.0	219.0	201.9	188.8	177.0	165.2	163.9	161.3	161.3
70°	215.1	207.2	200.6	182.3	167.9	153.4	150.8	146.9	142.9	141.6	139.0
72.5°	179.7	173.1	165.2	149.5	135.1	131.1	128.5	125.9	122.0	120.6	119.3
75°	145.6	136.4	131.1	116.7	112.8	110.2	107.5	103.6	101.0	99.7	97.0
77.5°	111.5	102.3	102.3	94.4	91.8	87.9	85.2	82.6	81.3	78.7	78.7
80°	78.7	78.7	76.1	72.1	68.2	66.9	62.9	61.6	60.3	61.6	59.0
82.5°	57.7	52.5	52.5	49.8	47.2	45.9	43.3	43.3	42.0	42.0	42.0
85°	32.8	32.8	31.5	28.8	27.5	27.5	26.2	26.2	24.9	24.9	23.6
87.5°	13.1	11.8	13.1	11.8	11.8	10.5	10.5	10.5	9.2	10.5	9.2
90°	13.9	15.6	17.3	23.1	31.2	38.1	39.2	38.1	36.9	34.6	36.9
92.5°	48.5	54.8	61.2	92.3	136.2	175.5	177.8	148.9	116.6	99.3	86.6
95°	85.4	99.2	113.1	166.2	266.6	400.6	452.5	395.9	302.4	232.0	183.5
97.5°	115.4	131.0	146.6	214.7	354.4	570.2	737.6	743.4	618.7	494.1	377.5
100°	144.3	160.4	176.6	237.8	378.6	628.0	911.9	1078.1	1053.9	910.8	752.6
102.5°	170.8	187.0	203.2	258.6	379.8	606.0	917.7	1202.8	1339.0	1334.4	1229.4
105°	196.2	212.4	228.6	282.8	385.5	576.0	855.4	1162.4	1402.5	1532.9	1547.9
107.5°	221.6	237.8	254.0	307.0	398.2	559.8	797.6	1077.0	1334.4	1528.3	1641.4
110°	247.0	263.8	280.5	331.3	414.4	555.2	758.4	997.3	1240.9	1447.5	1595.3

TEST NUMBER: P1010265

CATALOG NUMBER: S122RDIP-B865D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	271.3	288.6	305.9	354.4	431.7	556.4	733.0	941.9	1155.5	1351.7	1512.2
115°	297.8	313.4	329.0	378.6	449.0	561.0	715.7	898.1	1088.5	1266.3	1417.5
117.5°	322.1	338.2	354.4	400.6	467.5	567.9	706.4	868.1	1033.1	1192.4	1333.2
120°	346.3	362.5	378.6	423.6	486.0	574.9	698.4	845.0	993.9	1137.0	1259.4
122.5°	370.5	387.2	404.0	445.6	502.1	582.9	693.7	825.3	962.7	1090.8	1205.1
125°	393.6	409.8	425.9	467.5	519.4	591.0	688.0	806.9	932.7	1051.6	1153.2
127.5°	414.4	431.2	447.9	488.3	535.6	599.1	684.5	789.6	902.7	1012.3	1109.3
130°	434.0	450.2	466.3	506.7	550.6	608.3	682.2	772.2	873.8	973.1	1064.3
132.5°	452.5	468.6	484.8	522.9	565.6	617.6	681.1	758.4	846.1	936.2	1018.1
135°	468.7	484.8	501.0	537.9	578.3	624.5	679.9	745.7	820.7	896.9	973.1
137.5°	483.7	498.7	513.7	550.6	588.7	631.4	679.9	736.5	799.9	865.7	928.1
140°	496.4	511.4	526.4	561.0	596.8	636.0	678.7	728.4	780.3	835.7	888.8
142.5°	507.9	521.8	535.6	569.1	603.7	639.5	678.7	720.3	764.2	809.2	853.0
145°	520.6	533.3	546.0	577.2	609.5	641.8	676.4	713.4	749.2	787.2	823.0
147.5°	531.0	542.6	554.1	584.1	612.9	643.0	673.0	706.4	737.6	768.8	797.6
150°	541.4	551.8	562.2	588.7	615.3	641.8	669.5	697.2	724.9	750.3	774.6
152.5°	551.8	561.0	570.2	593.3	616.4	639.5	663.7	689.1	712.2	735.3	754.9
155°	561.0	569.6	578.3	597.9	617.6	637.2	656.8	678.7	700.7	719.1	736.5
157.5°	569.1	576.6	584.1	601.4	617.6	632.6	649.9	669.5	686.8	703.0	718.0
160°	577.2	583.6	589.9	603.7	617.6	629.1	643.0	659.1	674.1	686.8	699.5
162.5°	584.1	588.7	593.3	604.9	616.4	625.6	637.2	649.9	661.4	671.8	682.2
165°	588.7	592.2	595.6	606.0	614.1	621.0	629.1	639.5	648.7	656.8	664.9
167.5°	593.3	595.6	597.9	606.0	612.9	616.4	622.2	629.1	636.0	643.0	648.7
170°	595.6	597.4	599.1	604.9	610.6	612.9	616.4	621.0	626.8	630.3	634.9
172.5°	597.9	599.0	600.2	603.7	607.2	608.3	609.5	612.9	616.4	618.7	622.2
175°	599.1	599.7	600.2	602.6	604.9	603.7	604.9	606.0	609.5	610.6	611.8
177.5°	600.2	600.2	600.2	601.4	603.7	601.4	600.2	601.4	603.7	603.7	604.9
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P1010265

CATALOG NUMBER: S122RDIP-B865D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0
2.5°	1805.7	1803.1	1795.2	1797.8	1793.9	1793.9	1791.3	1791.3	1791.3	1797.8	1793.9
5°	1707.4	1698.2	1689.0	1685.1	1681.1	1677.2	1677.2	1675.9	1687.7	1685.1	1695.6
7.5°	1585.4	1582.8	1564.4	1564.4	1557.9	1555.2	1561.8	1563.1	1564.4	1567.1	1573.6
10°	1476.6	1470.0	1443.8	1446.4	1442.5	1437.2	1441.2	1438.5	1447.7	1450.3	1447.7
12.5°	1348.1	1336.3	1307.4	1293.0	1277.2	1265.4	1279.9	1269.4	1306.1	1316.6	1345.4
15°	1177.6	1155.3	1135.6	1135.6	1121.2	1110.7	1117.3	1129.1	1136.9	1148.7	1154.0
17.5°	1063.5	1054.3	1038.6	1029.4	1025.5	1021.5	1021.5	1026.8	1043.8	1042.5	1053.0
20°	966.5	961.2	953.3	941.5	937.6	935.0	935.0	935.0	946.8	957.3	963.8
22.5°	899.6	895.6	890.4	874.7	866.8	864.2	870.7	874.7	883.8	891.7	898.3
25°	832.7	823.5	814.3	809.1	805.2	805.2	807.8	809.1	813.0	817.0	824.8
27.5°	777.6	771.1	758.0	743.5	743.5	739.6	742.2	744.8	754.0	767.1	773.7
30°	716.0	714.7	709.4	704.2	698.9	696.3	701.6	705.5	706.8	713.4	713.4
32.5°	671.4	662.2	653.0	647.8	645.2	643.9	645.2	650.4	650.4	658.3	667.5
35°	626.8	621.6	612.4	603.2	600.6	594.0	599.3	604.5	613.7	617.6	621.6
37.5°	578.3	571.7	567.8	565.2	559.9	561.3	557.3	565.2	573.1	571.7	574.4
40°	541.6	529.8	518.0	516.7	515.4	514.0	514.0	515.4	520.6	525.8	533.7
42.5°	494.4	490.4	480.0	469.5	466.8	464.2	461.6	466.8	477.3	486.5	490.4
45°	445.9	440.6	438.0	430.1	424.9	423.6	420.9	427.5	436.7	440.6	443.2
47.5°	401.3	400.0	392.1	393.4	389.5	390.8	389.5	393.4	393.4	397.3	400.0
50°	371.1	367.2	363.2	360.6	356.7	356.7	355.4	356.7	361.9	367.2	365.9
52.5°	340.9	334.4	333.1	331.8	329.1	331.8	327.8	329.1	334.4	337.0	335.7
55°	305.5	304.2	301.6	299.0	297.7	296.4	296.4	296.4	301.6	305.5	306.9
57.5°	278.0	271.4	266.2	266.2	261.0	259.6	262.3	263.6	267.5	270.1	272.8
60°	240.0	237.4	229.5	225.6	217.7	216.4	216.4	221.6	228.2	237.4	240.0
62.5°	199.3	195.4	194.1	194.1	194.1	194.1	194.1	194.1	194.1	195.4	195.4
65°	177.0	178.3	177.0	175.7	177.0	177.0	175.7	175.7	175.7	177.0	178.3
67.5°	158.7	157.4	158.7	157.4	156.0	156.0	154.7	156.0	157.4	158.7	158.7
70°	137.7	137.7	136.4	137.7	136.4	135.1	133.8	133.8	136.4	137.7	137.7
72.5°	118.0	118.0	116.7	116.7	114.1	114.1	115.4	114.1	114.1	118.0	118.0
75°	98.4	97.0	95.7	95.7	94.4	94.4	94.4	93.1	95.7	95.7	97.0
77.5°	77.4	77.4	77.4	76.1	76.1	74.7	74.7	76.1	76.1	76.1	77.4
80°	59.0	59.0	59.0	57.7	56.4	56.4	56.4	56.4	56.4	57.7	56.4
82.5°	40.7	40.7	40.7	40.7	40.7	39.3	39.3	39.3	40.7	40.7	39.3
85°	24.9	23.6	24.9	24.9	23.6	24.9	23.6	23.6	22.3	22.3	23.6
87.5°	10.5	9.2	7.9	7.9	9.2	7.9	7.9	7.9	9.2	7.9	7.9
90°	37.5	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1	38.1	37.5
92.5°	81.9	77.3	76.2	71.6	72.7	70.4	72.7	71.6	76.2	77.3	81.9
95°	170.8	158.1	143.1	133.9	130.4	131.6	130.4	133.9	143.1	158.1	170.8
97.5°	342.8	308.2	263.2	240.1	227.4	220.5	227.4	240.1	263.2	308.2	342.8
100°	682.8	612.9	517.1	467.5	434.0	413.2	434.0	467.5	517.1	612.9	682.8
102.5°	1154.4	1079.3	973.1	879.6	835.7	805.7	835.7	879.6	973.1	1079.3	1154.4
105°	1528.9	1509.9	1438.3	1366.7	1317.1	1300.9	1317.1	1366.7	1438.3	1509.9	1528.9
107.5°	1664.5	1687.6	1686.5	1676.1	1661.1	1634.5	1661.1	1676.1	1686.5	1687.6	1664.5
110°	1642.6	1689.9	1739.6	1761.5	1771.9	1770.7	1771.9	1761.5	1739.6	1689.9	1642.6

TEST NUMBER: P1010265

CATALOG NUMBER: S122RDIP-B865D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1568.2	1624.1	1698.0	1738.4	1760.3	1768.4	1760.3	1738.4	1698.0	1624.1	1568.2
115°	1477.0	1536.4	1618.4	1671.5	1701.5	1711.9	1701.5	1671.5	1618.4	1536.4	1477.0
117.5°	1389.8	1446.4	1530.6	1587.2	1618.4	1626.4	1618.4	1587.2	1530.6	1446.4	1389.8
120°	1311.9	1364.4	1445.2	1499.5	1532.9	1544.5	1532.9	1499.5	1445.2	1364.4	1311.9
122.5°	1251.3	1297.5	1367.9	1421.0	1449.8	1459.1	1449.8	1421.0	1367.9	1297.5	1251.3
125°	1196.4	1239.7	1306.7	1350.6	1379.4	1388.7	1379.4	1350.6	1306.7	1239.7	1196.4
127.5°	1149.7	1190.1	1249.0	1290.5	1315.9	1322.9	1315.9	1290.5	1249.0	1190.1	1149.7
130°	1102.4	1140.5	1197.0	1236.3	1259.4	1268.6	1259.4	1236.3	1197.0	1140.5	1102.4
132.5°	1053.3	1088.5	1143.9	1183.2	1204.0	1212.0	1204.0	1183.2	1143.9	1088.5	1053.3
135°	1005.4	1037.7	1087.4	1125.5	1146.2	1150.9	1146.2	1125.5	1087.4	1037.7	1005.4
137.5°	957.0	985.8	1033.1	1066.6	1085.1	1092.0	1085.1	1066.6	1033.1	985.8	957.0
140°	914.2	939.6	976.6	1006.6	1023.9	1030.8	1023.9	1006.6	976.6	939.6	914.2
142.5°	873.2	893.4	928.1	954.6	969.6	969.6	969.6	954.6	928.1	893.4	873.2
145°	839.8	856.5	884.2	903.8	915.4	918.8	915.4	903.8	884.2	856.5	839.8
147.5°	810.3	823.0	847.3	863.4	871.5	873.8	871.5	863.4	847.3	823.0	810.3
150°	785.0	795.3	812.6	826.5	833.4	834.6	833.4	826.5	812.6	795.3	785.0
152.5°	763.6	772.2	784.9	796.5	801.1	801.1	801.1	796.5	784.9	772.2	763.6
155°	742.8	749.2	761.9	769.9	774.6	772.2	774.6	769.9	761.9	749.2	742.8
157.5°	723.2	728.4	737.6	744.5	746.8	746.8	746.8	744.5	737.6	728.4	723.2
160°	703.6	707.6	715.7	721.5	722.6	722.6	722.6	721.5	715.7	707.6	703.6
162.5°	685.1	688.0	696.1	699.5	700.7	699.5	700.7	699.5	696.1	688.0	685.1
165°	667.2	669.5	674.1	678.7	678.7	677.6	678.7	678.7	674.1	669.5	667.2
167.5°	651.0	653.3	655.7	658.0	658.0	656.8	658.0	658.0	655.7	653.3	651.0
170°	636.0	637.2	638.3	641.8	640.6	638.3	640.6	641.8	638.3	637.2	636.0
172.5°	622.8	623.3	624.5	625.6	624.5	623.3	624.5	625.6	624.5	623.3	622.8
175°	612.3	612.9	612.9	614.1	612.9	610.6	612.9	614.1	612.9	612.9	612.3
177.5°	604.9	604.9	604.9	604.9	603.7	601.4	603.7	604.9	604.9	604.9	604.9
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P1010265

CATALOG NUMBER: S122RDIP-B865D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0	1887.0
2.5°	1797.8	1804.4	1801.8	1787.4	1801.8	1805.7	1813.6	1821.5	1826.7	1834.6	1841.1
5°	1685.1	1698.2	1706.1	1698.2	1724.4	1728.3	1746.7	1757.2	1772.9	1786.0	1796.5
7.5°	1578.9	1589.3	1605.1	1607.7	1623.4	1641.8	1668.0	1694.3	1719.2	1732.3	1744.1
10°	1464.8	1483.1	1506.7	1501.5	1525.1	1553.9	1581.5	1623.4	1644.4	1668.0	1689.0
12.5°	1350.7	1362.5	1394.0	1404.4	1438.5	1460.8	1498.9	1525.1	1577.5	1605.1	1623.4
15°	1151.4	1199.9	1239.2	1286.4	1331.0	1373.0	1407.1	1454.3	1500.2	1521.2	1551.3
17.5°	1060.9	1083.2	1106.8	1130.4	1188.1	1262.8	1323.1	1374.3	1413.6	1441.2	1476.6
20°	966.5	988.7	1015.0	1037.3	1072.7	1126.4	1201.2	1289.0	1336.3	1365.1	1399.2
22.5°	899.6	920.6	937.6	957.3	984.8	1024.2	1080.5	1189.4	1252.3	1287.7	1317.9
25°	827.5	853.7	872.0	886.5	908.8	952.0	997.9	1059.6	1172.3	1199.9	1241.8
27.5°	777.6	785.5	806.5	828.8	851.1	874.7	921.9	974.3	1050.4	1110.7	1161.8
30°	718.6	738.3	758.0	767.1	786.8	820.9	849.7	906.1	965.1	1012.4	1074.0
32.5°	674.0	685.8	698.9	721.2	739.6	763.2	792.0	839.3	889.1	919.2	966.5
35°	624.2	632.1	659.6	668.8	687.1	710.7	739.6	776.3	830.1	853.7	887.8
37.5°	577.0	595.3	603.2	624.2	641.2	664.8	685.8	727.8	763.2	790.7	822.2
40°	540.3	548.1	562.6	580.9	595.3	613.7	639.9	670.1	708.1	730.4	758.0
42.5°	495.7	502.2	520.6	531.1	554.7	571.7	587.5	624.2	658.3	675.3	702.9
45°	447.2	462.9	474.7	495.7	508.8	529.8	549.5	575.7	607.2	626.8	642.6
47.5°	405.2	420.9	432.7	452.4	473.4	482.6	503.6	531.1	559.9	575.7	598.0
50°	371.1	376.4	398.6	407.8	430.1	448.5	462.9	486.5	518.0	527.2	545.5
52.5°	338.3	342.3	356.7	368.5	388.2	403.9	422.3	444.5	470.8	485.2	499.6
55°	309.5	312.1	318.7	331.8	344.9	364.6	381.6	402.6	424.9	440.6	453.7
57.5°	276.7	281.9	287.2	295.1	308.2	326.5	344.9	364.6	382.9	393.4	410.4
60°	238.7	246.5	255.7	264.9	274.1	287.2	308.2	326.5	343.6	352.8	365.9
62.5°	198.0	213.7	221.6	232.1	240.0	251.8	267.5	288.5	300.3	312.1	322.6
65°	178.3	179.7	181.0	191.5	205.9	217.7	232.1	247.8	266.2	274.1	281.9
67.5°	158.7	160.0	162.6	163.9	169.2	182.3	198.0	215.1	229.5	234.7	242.6
70°	139.0	139.0	144.2	145.6	146.9	148.2	161.3	178.3	191.5	198.0	207.2
72.5°	118.0	119.3	122.0	123.3	125.9	128.5	132.4	141.6	157.4	163.9	174.4
75°	97.0	98.4	99.7	101.0	104.9	106.2	110.2	115.4	122.0	129.8	136.4
77.5°	77.4	77.4	78.7	81.3	83.9	85.2	89.2	91.8	94.4	98.4	103.6
80°	57.7	59.0	59.0	61.6	61.6	62.9	64.3	68.2	70.8	73.4	76.1
82.5°	39.3	42.0	42.0	42.0	43.3	44.6	45.9	45.9	48.5	49.8	53.8
85°	23.6	24.9	24.9	24.9	23.6	26.2	26.2	27.5	27.5	27.5	28.8
87.5°	9.2	7.9	9.2	9.2	9.2	10.5	9.2	9.2	10.5	11.8	11.8
90°	36.9	34.6	36.9	38.1	39.2	38.1	31.2	23.1	17.3	15.6	13.9
92.5°	86.6	99.3	116.6	148.9	177.8	175.5	136.2	92.3	61.2	54.8	48.5
95°	183.5	232.0	302.4	395.9	452.5	400.6	266.6	166.2	113.1	99.2	85.4
97.5°	377.5	494.1	618.7	743.4	737.6	570.2	354.4	214.7	146.6	131.0	115.4
100°	752.6	910.8	1053.9	1078.1	911.9	628.0	378.6	237.8	176.6	160.4	144.3
102.5°	1229.4	1334.4	1339.0	1202.8	917.7	606.0	379.8	258.6	203.2	187.0	170.8
105°	1547.9	1532.9	1402.5	1162.4	855.4	576.0	385.5	282.8	228.6	212.4	196.2
107.5°	1641.4	1528.3	1334.4	1077.0	797.6	559.8	398.2	307.0	254.0	237.8	221.6
110°	1595.3	1447.5	1240.9	997.3	758.4	555.2	414.4	331.3	280.5	263.8	247.0

TEST NUMBER: P1010265

CATALOG NUMBER: S122RDIP-B865D1080UB40-4FO-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1512.2	1351.7	1155.5	941.9	733.0	556.4	431.7	354.4	305.9	288.6	271.3
115°	1417.5	1266.3	1088.5	898.1	715.7	561.0	449.0	378.6	329.0	313.4	297.8
117.5°	1333.2	1192.4	1033.1	868.1	706.4	567.9	467.5	400.6	354.4	338.2	322.1
120°	1259.4	1137.0	993.9	845.0	698.4	574.9	486.0	423.6	378.6	362.5	346.3
122.5°	1205.1	1090.8	962.7	825.3	693.7	582.9	502.1	445.6	404.0	387.2	370.5
125°	1153.2	1051.6	932.7	806.9	688.0	591.0	519.4	467.5	425.9	409.8	393.6
127.5°	1109.3	1012.3	902.7	789.6	684.5	599.1	535.6	488.3	447.9	431.2	414.4
130°	1064.3	973.1	873.8	772.2	682.2	608.3	550.6	506.7	466.3	450.2	434.0
132.5°	1018.1	936.2	846.1	758.4	681.1	617.6	565.6	522.9	484.8	468.6	452.5
135°	973.1	896.9	820.7	745.7	679.9	624.5	578.3	537.9	501.0	484.8	468.7
137.5°	928.1	865.7	799.9	736.5	679.9	631.4	588.7	550.6	513.7	498.7	483.7
140°	888.8	835.7	780.3	728.4	678.7	636.0	596.8	561.0	526.4	511.4	496.4
142.5°	853.0	809.2	764.2	720.3	678.7	639.5	603.7	569.1	535.6	521.8	507.9
145°	823.0	787.2	749.2	713.4	676.4	641.8	609.5	577.2	546.0	533.3	520.6
147.5°	797.6	768.8	737.6	706.4	673.0	643.0	612.9	584.1	554.1	542.6	531.0
150°	774.6	750.3	724.9	697.2	669.5	641.8	615.3	588.7	562.2	551.8	541.4
152.5°	754.9	735.3	712.2	689.1	663.7	639.5	616.4	593.3	570.2	561.0	551.8
155°	736.5	719.1	700.7	678.7	656.8	637.2	617.6	597.9	578.3	569.6	561.0
157.5°	718.0	703.0	686.8	669.5	649.9	632.6	617.6	601.4	584.1	576.6	569.1
160°	699.5	686.8	674.1	659.1	643.0	629.1	617.6	603.7	589.9	583.6	577.2
162.5°	682.2	671.8	661.4	649.9	637.2	625.6	616.4	604.9	593.3	588.7	584.1
165°	664.9	656.8	648.7	639.5	629.1	621.0	614.1	606.0	595.6	592.2	588.7
167.5°	648.7	643.0	636.0	629.1	622.2	616.4	612.9	606.0	597.9	595.6	593.3
170°	634.9	630.3	626.8	621.0	616.4	612.9	610.6	604.9	599.1	597.4	595.6
172.5°	622.2	618.7	616.4	612.9	609.5	608.3	607.2	603.7	600.2	599.0	597.9
175°	611.8	610.6	609.5	606.0	604.9	603.7	604.9	602.6	600.2	599.7	599.1
177.5°	604.9	603.7	603.7	601.4	600.2	601.4	603.7	601.4	600.2	600.2	600.2
180°	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2	600.2

TEST NUMBER: P1010265

CATALOG NUMBER: S122RDIP-B865D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1887.0	1887.0	1887.0	1887.0
2.5°	1852.9	1849.0	1872.6	1898.8
5°	1814.9	1821.5	1851.6	1888.3
7.5°	1775.6	1790.0	1825.4	1873.9
10°	1720.5	1746.7	1800.5	1850.3
12.5°	1666.7	1702.1	1753.3	1812.3
15°	1606.4	1645.7	1708.7	1779.5
17.5°	1539.5	1584.1	1657.5	1734.9
20°	1468.7	1527.7	1605.1	1689.0
22.5°	1390.0	1460.8	1540.8	1633.9
25°	1314.0	1391.3	1471.3	1578.9
27.5°	1239.2	1315.3	1404.4	1513.3
30°	1164.5	1234.0	1329.7	1446.4
32.5°	1084.5	1156.6	1257.6	1376.9
35°	1011.0	1083.2	1177.6	1295.6
37.5°	932.4	1009.7	1100.2	1222.2
40°	840.6	931.1	1018.9	1135.6
42.5°	764.5	860.2	945.5	1055.6
45°	704.2	794.7	865.5	973.0
47.5°	647.8	721.2	793.4	893.0
50°	594.0	650.4	725.2	814.3
52.5°	539.0	587.5	651.7	735.7
55°	489.1	535.0	592.7	657.0
57.5°	443.2	476.0	533.7	591.4
60°	392.1	426.2	470.8	519.3
62.5°	348.8	375.0	417.0	457.7
65°	302.9	327.8	359.3	397.3
67.5°	261.0	283.2	308.2	338.3
70°	222.9	240.0	258.3	284.6
72.5°	182.3	200.6	217.7	238.7
75°	149.5	157.4	171.8	186.2
77.5°	115.4	125.9	133.8	145.6
80°	82.6	91.8	94.4	103.6
82.5°	55.1	60.3	65.6	68.2
85°	31.5	34.1	39.3	40.7
87.5°	11.8	13.1	15.7	18.4
90°	11.5	9.2	4.6	1.2
92.5°	39.2	33.5	24.2	17.3
95°	67.0	56.6	45.0	40.4
97.5°	94.7	79.6	67.0	60.0
100°	121.2	102.7	92.3	88.9
102.5°	146.6	128.1	117.7	115.4
105°	170.8	153.5	145.4	140.8
107.5°	196.2	180.1	172.0	168.5
110°	222.8	207.8	200.9	196.2

TEST NUMBER: P1010265

CATALOG NUMBER: S122RDIP-B865D1080UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	248.2	234.3	226.2	221.6
115°	274.7	260.9	254.0	248.2
117.5°	300.1	287.4	280.5	275.9
120°	323.2	312.8	305.9	301.3
122.5°	347.5	335.9	329.0	325.5
125°	370.5	356.7	349.8	346.3
127.5°	392.5	377.5	368.2	363.6
130°	410.9	394.8	383.2	378.6
132.5°	428.3	410.9	398.2	392.5
135°	442.1	424.8	410.9	406.3
137.5°	457.1	438.6	424.8	419.0
140°	471.0	452.5	438.6	434.0
142.5°	483.7	465.2	452.5	449.0
145°	497.5	480.2	468.7	464.0
147.5°	511.4	495.2	483.7	480.2
150°	524.1	509.1	499.8	496.4
152.5°	535.6	522.9	513.7	512.5
155°	548.3	535.6	528.7	527.5
157.5°	558.7	547.1	541.4	540.2
160°	567.9	558.7	554.1	552.9
162.5°	576.0	569.1	564.5	565.6
165°	582.9	576.0	573.7	574.9
167.5°	588.7	584.1	581.8	582.9
170°	593.3	589.9	588.7	591.0
172.5°	596.8	593.3	594.5	595.6
175°	599.1	596.8	597.9	599.1
177.5°	600.2	597.9	599.1	601.4
180°	600.2	600.2	600.2	600.2

(END OF REPORT)