

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010378

Luminaire Tested: S122RDIP-B865D925UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010378
REPORT IS A COMBINATION OF REPORTS P988803 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B865D925UB35-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6891.0 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010378

CATALOG NUMBER: S122RDIP-B865D925UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1010378

CATALOG NUMBER: S122RDIP-B865D925UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	107	107	107	107	98	98	98	98		82	82	82		68	68	68		54	54	54
1	98	94	90	87	90	87	84	81		73	71	69		61	59	58		49	48	47
2	90	83	77	72	83	77	72	68		65	61	58		54	52	49		44	42	41
3	83	74	67	61	76	68	62	57		58	54	50		49	45	43		40	38	36
4	76	66	58	53	70	61	55	50		52	47	43		44	40	37		36	34	32
5	70	59	51	46	64	55	48	43		47	42	38		40	36	33		33	30	28
6	65	53	46	40	60	50	43	38		43	38	34		36	32	29		30	27	25
7	60	48	41	36	55	45	39	34		39	34	30		33	29	26		28	25	23
8	56	44	37	32	52	41	35	30		36	31	27		31	27	24		26	23	21
9	52	41	33	29	48	38	32	27		33	28	24		28	25	22		24	21	19
10	49	37	31	26	45	35	29	25		31	26	22		26	23	20		23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30172	30172	30172	30172
5°	30242	32048	30348	25603
10°	29909	33873	30122	21143
15°	29261	33885	29757	15882
20°	28480	28009	29100	13103
25°	27533	17501	28129	11147
30°	26324	11206	27041	9597
35°	24854	8612	25659	8212
40°	23216	7238	24208	7183
45°	21467	6161	22362	6030
50°	19671	5235	20590	5216
55°	17682	4549	18636	4490
60°	15916	3469	16762	3428
65°	14270	2610	15116	2961
70°	12446	2086	13425	2413
75°	10522	1598	11485	1826
80°	8351	1087	8990	1198
85°	5806	560	6357	593

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 27600 cd/sqm

TEST NUMBER: P1010378

CATALOG NUMBER: S122RDIP-B865D925UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.8	2.6
10°-20°	504.7	7.3
20°-30°	649.5	9.4
30°-40°	616.2	8.9
40°-50°	528.1	7.7
50°-60°	402.2	5.8
60°-70°	253.6	3.7
70°-80°	126.5	1.8
80°-90°	35.8	0.5
90°-100°	201.2	2.9
100°-110°	708.4	10.3
110°-120°	744.0	10.8
120°-130°	612.1	8.9
130°-140°	491.7	7.1
140°-150°	371.4	5.4
150°-160°	261.1	3.8
160°-170°	153.7	2.2
170°-180°	50.0	0.7
0°-30°	1334.9	19.4
0°-40°	1951.1	28.3
0°-60°	2881.3	41.8
0°-90°	3297.3	47.8
90°-120°	1653.6	24.0
90°-150°	3128.9	45.4
90°-180°	3594.0	52.2
0°-180°	6891.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1906	1906	1906	1906	1906	
5°	1907	2121	1914	1694	1907	181
15°	1798	2394	1828	1122	1798	506
25°	1595	1277	1629	813	1595	732
35°	1309	629	1351	600	1309	819
45°	983	437	1024	428	983	759
55°	664	303	699	299	664	598
65°	401	158	425	179	401	398
75°	188	84	205	95	188	204
85°	41	24	45	25	41	47
90°	1	33	1	33	1	5
95°	35	113	35	113	35	36
105°	121	1118	121	1118	121	129
115°	213	1472	213	1472	213	212
125°	298	1194	298	1194	298	265
135°	349	989	349	989	349	270
145°	399	790	399	790	399	250
155°	454	664	454	664	454	209
165°	494	582	494	582	494	139
175°	515	525	515	525	515	49
180°	516	516	516	516	516	

TEST NUMBER: P1010378

CATALOG NUMBER: S122RDIP-B865D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1918.0	1926.0	1930.0	1935.3	1947.2	1955.1	1967.0	1969.7	1968.4	1973.7	1959.1
5°	1907.4	1924.7	1940.6	1953.8	1975.0	1988.2	2002.8	2020.0	2024.0	2043.9	2032.0
7.5°	1892.9	1918.0	1940.6	1967.0	1998.8	2016.1	2038.6	2065.1	2077.0	2100.8	2107.5
10°	1869.0	1904.8	1943.2	1971.0	2014.7	2045.2	2066.4	2108.8	2136.6	2172.4	2167.1
12.5°	1830.6	1877.0	1928.6	1975.0	2032.0	2051.8	2091.6	2135.3	2171.0	2204.2	2233.3
15°	1797.5	1850.5	1907.4	1964.4	2029.3	2066.4	2106.1	2163.1	2201.5	2259.8	2285.0
17.5°	1752.5	1820.0	1887.6	1951.1	2028.0	2070.4	2119.4	2175.0	2232.0	2287.6	2307.5
20°	1706.1	1779.0	1851.8	1937.9	2025.3	2066.4	2116.7	2185.6	2241.2	2285.0	2285.0
22.5°	1650.5	1739.2	1822.7	1904.8	2000.2	2059.8	2111.4	2192.2	2232.0	2241.2	2205.5
25°	1594.8	1683.6	1775.0	1877.0	1985.6	2038.6	2096.9	2172.4	2185.6	2148.5	2055.8
27.5°	1528.6	1627.9	1731.3	1841.2	1955.1	2021.4	2074.3	2124.7	2099.5	2000.2	1855.8
30°	1461.0	1568.3	1684.9	1789.5	1927.3	1988.2	2033.3	2047.8	1968.4	1806.8	1620.0
32.5°	1390.8	1495.5	1618.7	1744.5	1883.6	1941.9	1971.0	1932.6	1786.9	1582.9	1355.1
35°	1308.7	1426.6	1555.1	1686.2	1824.0	1867.7	1884.9	1790.9	1604.1	1340.5	1114.0
37.5°	1234.5	1352.4	1490.2	1624.0	1757.8	1781.6	1764.4	1617.3	1380.2	1119.3	898.1
40°	1147.1	1272.9	1408.1	1557.7	1667.7	1674.3	1631.9	1441.2	1147.1	902.1	765.6
42.5°	1066.3	1193.5	1328.6	1480.9	1564.4	1541.8	1484.9	1234.5	957.7	777.5	667.6
45°	982.9	1103.4	1249.1	1384.2	1443.8	1390.8	1304.7	1038.5	804.0	668.9	584.2
47.5°	902.1	1014.7	1159.0	1288.8	1299.4	1239.8	1137.8	870.3	696.7	588.1	519.2
50°	822.6	935.2	1070.3	1177.6	1167.0	1084.9	969.6	756.4	605.3	519.2	462.3
52.5°	743.1	845.1	976.2	1061.0	1016.0	936.5	822.6	641.1	528.5	453.0	409.3
55°	663.6	759.0	871.6	941.8	870.3	778.9	698.1	549.7	458.3	397.4	364.3
57.5°	597.4	672.9	776.2	818.6	732.5	661.0	590.8	472.9	397.4	353.7	315.3
60°	524.5	593.4	678.2	703.4	614.6	556.3	496.7	400.0	340.4	302.0	276.8
62.5°	462.3	519.2	584.2	584.2	506.0	462.3	417.3	335.1	286.1	255.6	243.7
65°	401.4	442.4	488.8	483.5	417.3	378.8	343.1	276.8	239.8	218.6	206.6
67.5°	341.7	373.5	404.0	385.5	337.8	304.7	271.5	223.9	198.7	184.1	168.2
70°	287.4	312.6	328.5	311.3	263.6	235.8	211.9	180.1	160.3	141.7	132.5
72.5°	241.1	251.7	257.0	235.8	196.0	180.1	162.9	140.4	123.2	113.9	111.3
75°	188.1	197.4	193.4	177.5	144.4	132.5	119.2	103.3	99.3	94.0	91.4
77.5°	147.0	147.0	140.4	125.8	103.3	94.0	88.7	80.8	76.8	75.5	72.9
80°	104.6	103.3	99.3	83.5	70.2	64.9	64.9	59.6	58.3	55.6	55.6
82.5°	68.9	68.9	63.6	50.3	46.4	45.0	43.7	41.1	41.1	39.7	39.7
85°	41.1	38.4	31.8	27.8	26.5	26.5	25.2	23.8	25.2	23.8	23.8
87.5°	18.5	14.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6
90°	1.0	4.0	7.9	9.9	11.9	13.4	14.9	19.8	26.8	32.7	33.7
92.5°	14.9	20.8	28.8	33.7	41.7	47.2	52.6	79.4	117.1	150.8	152.8
95°	34.7	38.7	48.6	57.6	73.4	85.4	97.3	142.9	229.2	344.4	389.0
97.5°	51.6	57.6	68.5	81.4	99.2	112.6	126.0	184.6	304.7	490.2	634.1
100°	76.4	79.4	88.3	104.2	124.0	137.9	151.8	204.4	325.5	539.9	784.0
102.5°	99.2	101.2	110.2	126.0	146.9	160.8	174.7	222.3	326.5	521.0	788.9
105°	121.1	125.0	132.0	146.9	168.7	182.6	196.5	243.1	331.5	495.2	735.4
107.5°	144.9	147.9	154.8	168.7	190.5	204.4	218.3	264.0	342.4	481.3	685.7
110°	168.7	172.7	178.6	191.5	212.4	226.8	241.1	284.8	356.3	477.3	652.0

TEST NUMBER: P1010378

CATALOG NUMBER: S122RDIP-B865D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	190.5	194.5	201.5	213.4	233.2	248.1	263.0	304.7	371.1	478.3	630.2
115°	213.4	218.3	224.3	236.2	256.0	269.4	282.8	325.5	386.0	482.3	615.3
117.5°	237.2	241.1	247.1	258.0	276.9	290.8	304.7	344.4	401.9	488.2	607.3
120°	259.0	263.0	268.9	277.9	297.7	311.6	325.5	364.2	417.8	494.2	600.4
122.5°	279.8	282.8	288.8	298.7	318.6	333.0	347.3	383.1	431.7	501.1	596.4
125°	297.7	300.7	306.6	318.6	338.4	352.3	366.2	401.9	446.6	508.1	591.5
127.5°	312.6	316.6	324.5	337.4	356.3	370.6	385.0	419.8	460.5	515.0	588.5
130°	325.5	329.5	339.4	353.3	373.1	387.0	400.9	435.7	473.4	523.0	586.5
132.5°	337.4	342.4	353.3	368.2	389.0	402.9	416.8	449.5	486.3	530.9	585.5
135°	349.3	353.3	365.2	380.1	402.9	416.8	430.7	462.4	497.2	536.9	584.5
137.5°	360.2	365.2	377.1	393.0	415.8	428.7	441.6	473.4	506.1	542.8	584.5
140°	373.1	377.1	389.0	404.9	426.7	439.6	452.5	482.3	513.1	546.8	583.5
142.5°	386.0	389.0	399.9	415.8	436.6	448.6	460.5	489.2	519.0	549.8	583.5
145°	398.9	402.9	412.8	427.7	447.6	458.5	469.4	496.2	524.0	551.8	581.5
147.5°	412.8	415.8	425.7	439.6	456.5	466.4	476.3	502.1	527.0	552.8	578.6
150°	426.7	429.7	437.6	450.5	465.4	474.4	483.3	506.1	528.9	551.8	575.6
152.5°	440.6	441.6	449.5	460.5	474.4	482.3	490.2	510.1	529.9	549.8	570.6
155°	453.5	454.5	460.5	471.4	482.3	489.8	497.2	514.1	530.9	547.8	564.7
157.5°	464.4	465.4	470.4	480.3	489.2	495.6	502.1	517.0	530.9	543.8	558.7
160°	475.3	476.3	480.3	488.2	496.2	501.6	507.1	519.0	530.9	540.8	552.8
162.5°	486.3	485.3	489.2	495.2	502.1	506.1	510.1	520.0	529.9	537.9	547.8
165°	494.2	493.2	495.2	501.1	506.1	509.1	512.1	521.0	527.9	533.9	540.8
167.5°	501.1	500.2	502.1	506.1	510.1	512.1	514.1	521.0	527.0	529.9	534.9
170°	508.1	506.1	507.1	510.1	512.1	513.6	515.0	520.0	525.0	527.0	529.9
172.5°	512.1	511.1	510.1	513.1	514.1	515.0	516.0	519.0	522.0	523.0	524.0
175°	515.0	514.1	513.1	515.0	515.0	515.5	516.0	518.0	520.0	519.0	520.0
177.5°	517.0	515.0	514.1	516.0	516.0	516.0	516.0	517.0	519.0	517.0	516.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P1010378

CATALOG NUMBER: S122RDIP-B865D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1973.7	1976.3	1980.3	1998.8	2001.5	2006.8	2004.1	2004.1	2005.5	2002.8	2004.1
5°	2058.4	2062.4	2082.3	2104.8	2110.1	2104.8	2111.4	2120.7	2120.7	2120.7	2118.1
7.5°	2137.9	2152.5	2175.0	2208.1	2214.7	2221.4	2233.3	2225.3	2228.0	2239.9	2235.9
10°	2214.7	2235.9	2261.1	2288.9	2303.5	2312.8	2318.1	2330.0	2357.8	2326.0	2337.9
12.5°	2287.6	2318.1	2344.6	2375.0	2385.6	2397.5	2401.5	2412.1	2412.1	2410.8	2420.1
15°	2335.3	2363.1	2386.9	2406.8	2409.5	2406.8	2404.2	2405.5	2409.5	2393.6	2402.8
17.5°	2345.9	2348.5	2356.5	2348.5	2349.9	2322.0	2306.1	2302.2	2265.1	2266.4	2296.9
20°	2294.2	2249.2	2237.3	2193.6	2167.1	2095.5	2092.9	2073.0	1994.9	2018.7	2013.4
22.5°	2152.5	2075.7	1973.7	1923.3	1898.2	1822.7	1764.4	1723.3	1695.5	1667.7	1655.8
25°	1965.7	1841.2	1696.8	1597.5	1582.9	1512.7	1405.4	1355.1	1295.5	1276.9	1308.7
27.5°	1724.6	1563.0	1400.1	1247.8	1220.0	1156.4	1102.1	1066.3	997.4	993.5	996.1
30°	1397.5	1234.5	1098.1	998.8	929.9	900.7	865.0	838.5	810.7	821.3	823.9
32.5°	1148.4	993.5	866.3	813.3	781.5	763.0	732.5	715.3	703.4	699.4	698.1
35°	912.7	809.3	752.4	700.7	682.2	668.9	646.4	638.5	627.9	629.2	629.2
37.5°	781.5	695.4	653.0	626.5	609.3	602.7	588.1	580.2	573.6	570.9	574.9
40°	674.2	614.6	588.1	564.3	549.7	547.1	539.1	529.8	521.9	523.2	527.2
42.5°	596.1	561.6	529.8	511.3	500.7	496.7	490.1	483.5	483.5	479.5	478.2
45°	533.8	506.0	479.5	462.3	455.7	450.4	442.4	441.1	435.8	437.1	438.4
47.5°	478.2	455.7	435.8	418.6	412.0	410.6	402.7	397.4	397.4	396.1	394.7
50°	427.8	405.3	388.1	378.8	369.6	366.9	365.6	364.3	361.6	361.6	362.9
52.5°	386.8	364.3	351.0	343.1	337.8	335.1	335.1	333.8	333.8	333.8	332.5
55°	341.7	323.2	312.6	310.0	307.3	306.0	304.7	302.0	300.7	303.3	300.7
57.5°	299.4	292.7	283.5	280.8	274.2	274.2	270.2	267.6	264.9	267.6	267.6
60°	266.2	257.0	251.7	243.7	238.4	233.1	226.5	225.2	222.5	221.2	219.9
62.5°	231.8	223.9	210.6	198.7	190.7	185.4	182.8	181.5	181.5	180.1	180.1
65°	193.4	174.8	168.2	164.3	162.9	161.6	159.0	157.6	159.0	157.6	159.0
67.5°	151.0	148.4	144.4	141.7	140.4	139.1	139.1	137.8	137.8	137.8	137.8
70°	131.1	124.5	123.2	120.5	120.5	119.2	119.2	119.2	119.2	117.9	120.5
72.5°	108.6	104.6	103.3	102.0	102.0	102.0	100.7	100.7	100.7	99.3	100.7
75°	88.7	87.4	84.8	84.8	83.5	84.8	83.5	83.5	82.1	83.5	83.5
77.5°	71.5	70.2	68.9	68.9	67.6	67.6	67.6	67.6	67.6	67.6	68.9
80°	54.3	53.0	51.7	53.0	51.7	53.0	51.7	51.7	53.0	51.7	51.7
82.5°	39.7	38.4	38.4	37.1	37.1	37.1	37.1	37.1	37.1	37.1	37.1
85°	23.8	22.5	22.5	23.8	22.5	23.8	22.5	22.5	22.5	23.8	23.8
87.5°	10.6	11.9	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	11.9
90°	32.7	31.8	29.8	31.8	32.2	32.7	32.7	32.7	32.7	32.7	32.7
92.5°	128.0	100.2	85.3	74.4	70.4	66.5	65.5	61.5	62.5	60.5	62.5
95°	340.4	260.0	199.5	157.8	146.9	136.0	123.1	115.1	112.1	113.1	112.1
97.5°	639.1	531.9	424.7	324.5	294.8	265.0	226.3	206.4	195.5	189.5	195.5
100°	926.9	906.0	783.0	647.0	587.0	527.0	444.6	401.9	373.1	355.3	373.1
102.5°	1034.1	1151.2	1147.2	1056.9	992.4	927.9	836.6	756.2	718.5	692.7	718.5
105°	999.3	1205.7	1317.9	1330.8	1314.4	1298.0	1236.5	1175.0	1132.3	1118.4	1132.3
107.5°	925.9	1147.2	1313.9	1411.2	1431.1	1450.9	1449.9	1440.9	1428.0	1405.2	1428.0
110°	857.4	1066.8	1244.4	1371.5	1412.2	1452.8	1495.5	1514.4	1523.3	1522.3	1523.3

TEST NUMBER: P1010378

CATALOG NUMBER: S122RDIP-B865D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	809.8	993.4	1162.1	1300.0	1348.2	1396.3	1459.8	1494.5	1513.4	1520.3	1513.4
115°	772.1	935.8	1088.6	1218.6	1269.8	1320.9	1391.3	1437.0	1462.8	1471.7	1462.8
117.5°	746.3	888.2	1025.1	1146.2	1194.8	1243.4	1315.9	1364.5	1391.3	1398.3	1391.3
120°	726.4	854.4	977.5	1082.7	1127.8	1173.0	1242.5	1289.1	1317.9	1327.8	1317.9
122.5°	709.5	827.6	937.8	1036.0	1075.7	1115.4	1176.0	1221.6	1246.4	1254.4	1246.4
125°	693.7	801.8	904.1	991.4	1028.6	1065.8	1123.4	1161.1	1185.9	1193.8	1185.9
127.5°	678.8	776.0	870.3	953.7	988.4	1023.1	1073.8	1109.5	1131.3	1137.3	1131.3
130°	663.9	751.2	836.6	915.0	947.8	980.5	1029.1	1062.8	1082.7	1090.6	1082.7
132.5°	652.0	727.4	804.8	875.3	905.6	935.8	983.4	1017.2	1035.0	1042.0	1035.0
135°	641.1	705.6	771.1	836.6	864.4	892.1	934.8	967.6	985.4	989.4	985.4
137.5°	633.1	687.7	744.3	797.9	822.7	847.5	888.2	917.0	932.8	938.8	932.8
140°	626.2	670.8	718.5	764.1	786.0	807.8	839.5	865.4	880.2	886.2	880.2
142.5°	619.2	657.0	695.7	733.4	750.8	768.1	797.9	820.7	833.6	833.6	833.6
145°	613.3	644.1	676.8	707.6	722.0	736.3	760.2	777.0	787.0	789.9	787.0
147.5°	607.3	634.1	660.9	685.7	696.7	707.6	728.4	742.3	749.2	751.2	749.2
150°	599.4	623.2	645.0	665.9	674.8	683.7	698.6	710.5	716.5	717.5	716.5
152.5°	592.4	612.3	632.1	649.0	656.4	663.9	674.8	684.7	688.7	688.7	688.7
155°	583.5	602.4	618.2	633.1	638.6	644.1	655.0	661.9	665.9	663.9	665.9
157.5°	575.6	590.5	604.4	617.3	621.8	626.2	634.1	640.1	642.1	642.1	642.1
160°	566.6	579.5	590.5	601.4	604.8	608.3	615.3	620.2	621.2	621.2	621.2
162.5°	558.7	568.6	577.6	586.5	589.0	591.5	598.4	601.4	602.4	601.4	602.4
165°	549.8	557.7	564.7	571.6	573.6	575.6	579.5	583.5	583.5	582.5	583.5
167.5°	540.8	546.8	552.8	557.7	559.7	561.7	563.7	565.7	565.7	564.7	565.7
170°	533.9	538.9	541.8	545.8	546.8	547.8	548.8	551.8	550.8	548.8	550.8
172.5°	527.0	529.9	531.9	534.9	535.4	535.9	536.9	537.9	536.9	535.9	536.9
175°	521.0	524.0	525.0	526.0	526.5	527.0	527.0	527.9	527.0	525.0	527.0
177.5°	517.0	519.0	519.0	520.0	520.0	520.0	520.0	520.0	519.0	517.0	519.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P1010378

CATALOG NUMBER: S122RDIP-B865D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	2009.4	2000.2	1997.5	2000.2	1997.5	1998.8	1989.6	1955.1	1964.4	1949.8	1957.8
5°	2123.3	2115.4	2098.2	2095.5	2092.9	2090.2	2077.0	2046.5	2034.6	2014.7	2013.4
7.5°	2232.0	2232.0	2218.7	2209.4	2197.5	2188.3	2171.0	2126.0	2107.5	2083.6	2070.4
10°	2339.3	2304.8	2319.4	2310.1	2281.0	2275.7	2243.9	2217.4	2181.6	2157.8	2136.6
12.5°	2416.1	2405.5	2392.2	2384.3	2376.3	2359.1	2337.9	2270.4	2251.8	2204.2	2180.3
15°	2413.4	2406.8	2410.8	2410.8	2408.1	2404.2	2386.9	2337.9	2306.1	2259.8	2218.7
17.5°	2283.6	2300.8	2318.1	2330.0	2356.5	2368.4	2384.3	2355.2	2335.3	2295.5	2251.8
20°	2057.1	2099.5	2149.8	2160.4	2184.3	2254.5	2286.3	2311.4	2319.4	2306.1	2270.4
22.5°	1741.9	1777.6	1899.5	1896.8	1931.3	2014.7	2107.5	2183.0	2242.6	2275.7	2262.4
25°	1364.3	1414.7	1479.6	1528.6	1641.2	1765.7	1880.9	2001.5	2104.8	2196.2	2218.7
27.5°	1031.9	1098.1	1149.8	1214.7	1271.6	1418.7	1567.0	1755.1	1875.6	2049.2	2139.2
30°	834.5	865.0	916.6	947.1	974.9	1087.5	1255.7	1441.2	1653.1	1853.1	2008.1
32.5°	712.6	733.8	772.2	785.5	814.6	890.1	996.1	1165.7	1384.2	1626.6	1830.6
35°	639.8	662.3	670.3	682.2	706.0	753.7	826.6	949.7	1147.1	1384.2	1627.9
37.5°	577.5	589.5	612.0	619.9	627.9	663.6	712.6	798.7	929.9	1124.6	1394.8
40°	533.8	540.4	552.4	559.0	564.3	589.5	633.2	691.4	788.1	936.5	1185.5
42.5°	487.5	495.4	503.4	511.3	517.9	537.8	564.3	619.9	684.8	797.4	977.6
45°	442.4	447.7	457.0	462.3	471.6	487.5	511.3	549.7	608.0	679.5	825.2
47.5°	401.4	408.0	412.0	418.6	425.2	442.4	464.9	490.1	537.8	608.0	714.0
50°	364.3	372.2	377.5	378.8	384.1	400.0	418.6	446.4	476.9	531.2	623.9
52.5°	337.8	339.1	343.1	348.4	347.0	356.3	373.5	394.7	426.5	470.2	537.8
55°	307.3	311.3	313.9	315.3	315.3	323.2	332.5	352.3	377.5	413.3	470.2
57.5°	268.9	272.9	280.8	283.5	287.4	291.4	295.4	308.6	329.8	364.3	410.6
60°	229.2	231.8	239.8	245.1	247.7	258.3	263.6	274.2	286.1	311.3	355.0
62.5°	184.1	186.8	190.7	196.0	201.3	217.2	230.5	241.1	250.4	267.6	303.3
65°	160.3	161.6	164.3	165.6	166.9	173.5	185.4	200.0	217.2	230.5	251.7
67.5°	139.1	140.4	141.7	144.4	145.7	147.0	152.3	156.3	173.5	192.1	208.0
70°	119.2	121.9	123.2	123.2	124.5	127.2	129.8	135.1	140.4	149.7	169.6
72.5°	100.7	102.0	104.6	104.6	104.6	107.3	109.9	112.6	115.2	120.5	128.5
75°	83.5	86.1	86.1	86.1	87.4	87.4	90.1	92.7	95.4	99.3	102.0
77.5°	68.9	68.9	68.9	68.9	70.2	70.2	71.5	74.2	75.5	76.8	79.5
80°	51.7	53.0	53.0	53.0	54.3	54.3	54.3	57.0	58.3	58.3	60.9
82.5°	38.4	38.4	38.4	39.7	38.4	39.7	39.7	41.1	39.7	41.1	42.4
85°	23.8	23.8	23.8	25.2	25.2	25.2	25.2	25.2	25.2	25.2	26.5
87.5°	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9	13.2	11.9	11.9
90°	32.7	32.7	32.7	32.2	31.8	29.8	31.8	32.7	33.7	32.7	26.8
92.5°	61.5	65.5	66.5	70.4	74.4	85.3	100.2	128.0	152.8	150.8	117.1
95°	115.1	123.1	136.0	146.9	157.8	199.5	260.0	340.4	389.0	344.4	229.2
97.5°	206.4	226.3	265.0	294.8	324.5	424.7	531.9	639.1	634.1	490.2	304.7
100°	401.9	444.6	527.0	587.0	647.0	783.0	906.0	926.9	784.0	539.9	325.5
102.5°	756.2	836.6	927.9	992.4	1056.9	1147.2	1151.2	1034.1	788.9	521.0	326.5
105°	1175.0	1236.5	1298.0	1314.4	1330.8	1317.9	1205.7	999.3	735.4	495.2	331.5
107.5°	1440.9	1449.9	1450.9	1431.1	1411.2	1313.9	1147.2	925.9	685.7	481.3	342.4
110°	1514.4	1495.5	1452.8	1412.2	1371.5	1244.4	1066.8	857.4	652.0	477.3	356.3

TEST NUMBER: P1010378

CATALOG NUMBER: S122RDIP-B865D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1494.5	1459.8	1396.3	1348.2	1300.0	1162.1	993.4	809.8	630.2	478.3	371.1
115°	1437.0	1391.3	1320.9	1269.8	1218.6	1088.6	935.8	772.1	615.3	482.3	386.0
117.5°	1364.5	1315.9	1243.4	1194.8	1146.2	1025.1	888.2	746.3	607.3	488.2	401.9
120°	1289.1	1242.5	1173.0	1127.8	1082.7	977.5	854.4	726.4	600.4	494.2	417.8
122.5°	1221.6	1176.0	1115.4	1075.7	1036.0	937.8	827.6	709.5	596.4	501.1	431.7
125°	1161.1	1123.4	1065.8	1028.6	991.4	904.1	801.8	693.7	591.5	508.1	446.6
127.5°	1109.5	1073.8	1023.1	988.4	953.7	870.3	776.0	678.8	588.5	515.0	460.5
130°	1062.8	1029.1	980.5	947.8	915.0	836.6	751.2	663.9	586.5	523.0	473.4
132.5°	1017.2	983.4	935.8	905.6	875.3	804.8	727.4	652.0	585.5	530.9	486.3
135°	967.6	934.8	892.1	864.4	836.6	771.1	705.6	641.1	584.5	536.9	497.2
137.5°	917.0	888.2	847.5	822.7	797.9	744.3	687.7	633.1	584.5	542.8	506.1
140°	865.4	839.5	807.8	786.0	764.1	718.5	670.8	626.2	583.5	546.8	513.1
142.5°	820.7	797.9	768.1	750.8	733.4	695.7	657.0	619.2	583.5	549.8	519.0
145°	777.0	760.2	736.3	722.0	707.6	676.8	644.1	613.3	581.5	551.8	524.0
147.5°	742.3	728.4	707.6	696.7	685.7	660.9	634.1	607.3	578.6	552.8	527.0
150°	710.5	698.6	683.7	674.8	665.9	645.0	623.2	599.4	575.6	551.8	528.9
152.5°	684.7	674.8	663.9	656.4	649.0	632.1	612.3	592.4	570.6	549.8	529.9
155°	661.9	655.0	644.1	638.6	633.1	618.2	602.4	583.5	564.7	547.8	530.9
157.5°	640.1	634.1	626.2	621.8	617.3	604.4	590.5	575.6	558.7	543.8	530.9
160°	620.2	615.3	608.3	604.8	601.4	590.5	579.5	566.6	552.8	540.8	530.9
162.5°	601.4	598.4	591.5	589.0	586.5	577.6	568.6	558.7	547.8	537.9	529.9
165°	583.5	579.5	575.6	573.6	571.6	564.7	557.7	549.8	540.8	533.9	527.9
167.5°	565.7	563.7	561.7	559.7	557.7	552.8	546.8	540.8	534.9	529.9	527.0
170°	551.8	548.8	547.8	546.8	545.8	541.8	538.9	533.9	529.9	527.0	525.0
172.5°	537.9	536.9	535.9	535.4	534.9	531.9	529.9	527.0	524.0	523.0	522.0
175°	527.9	527.0	527.0	526.5	526.0	525.0	524.0	521.0	520.0	519.0	520.0
177.5°	520.0	520.0	520.0	520.0	520.0	519.0	519.0	517.0	516.0	517.0	519.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P1010378

CATALOG NUMBER: S122RDIP-B865D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1945.9	1939.2	1939.2	1935.3	1935.3	1914.1	1914.1	1920.7	1912.7	1903.5	1890.2
5°	1996.2	1981.6	1977.6	1972.3	1955.1	1928.6	1918.0	1914.1	1898.2	1878.3	1855.8
7.5°	2043.9	2020.0	2008.1	1996.2	1973.7	1936.6	1915.4	1900.8	1877.0	1846.5	1817.4
10°	2090.2	2059.8	2029.3	2014.7	1982.9	1936.6	1906.1	1882.3	1847.8	1806.8	1765.7
12.5°	2132.6	2069.0	2063.7	2034.6	1988.2	1935.3	1888.9	1854.5	1810.7	1763.1	1715.4
15°	2169.7	2104.8	2073.0	2046.5	1985.6	1919.4	1870.3	1828.0	1769.7	1715.4	1657.1
17.5°	2188.3	2118.1	2096.9	2053.1	1990.9	1904.8	1838.6	1786.9	1723.3	1658.4	1592.2
20°	2206.8	2124.7	2090.2	2059.8	1975.0	1877.0	1802.8	1743.2	1673.0	1596.2	1523.3
22.5°	2216.1	2124.7	2083.6	2041.2	1959.1	1846.5	1759.1	1688.9	1606.8	1528.6	1441.2
25°	2200.2	2116.7	2067.7	2024.0	1931.3	1809.4	1708.7	1629.3	1541.8	1453.1	1364.3
27.5°	2160.4	2098.2	2041.2	1996.2	1892.9	1761.7	1655.8	1565.7	1475.6	1376.3	1286.2
30°	2086.3	2058.4	2013.4	1963.1	1850.5	1719.3	1593.5	1500.8	1401.4	1302.1	1208.0
32.5°	1971.0	1994.9	1965.7	1922.0	1800.1	1661.1	1527.3	1433.2	1324.6	1217.3	1131.2
35°	1830.6	1915.4	1899.5	1869.0	1747.2	1598.8	1465.0	1351.1	1242.5	1133.9	1047.8
37.5°	1677.0	1805.4	1818.7	1800.1	1686.2	1535.2	1388.2	1276.9	1165.7	1055.7	968.3
40°	1466.3	1663.7	1706.1	1714.0	1622.6	1458.4	1304.7	1196.1	1086.2	978.9	872.9
42.5°	1272.9	1522.0	1575.0	1608.1	1541.8	1382.9	1227.9	1107.4	998.8	902.1	796.1
45°	1091.5	1351.1	1437.2	1479.6	1450.4	1296.8	1136.5	1023.9	924.6	835.8	733.8
47.5°	904.7	1165.7	1286.2	1353.8	1353.8	1209.4	1049.1	937.8	842.5	766.9	676.9
50°	780.2	997.4	1121.9	1210.7	1234.5	1120.6	969.6	861.0	770.9	688.8	619.9
52.5°	665.0	859.7	963.0	1055.7	1124.6	1025.2	880.9	782.8	694.1	617.3	563.0
55°	574.9	720.6	814.6	916.6	993.5	928.6	794.8	699.4	622.6	559.0	512.6
57.5°	488.8	615.9	692.8	782.8	865.0	816.0	708.7	626.5	559.0	503.4	462.3
60°	415.9	519.2	578.9	649.1	751.1	716.6	627.9	552.4	498.1	447.7	413.3
62.5°	353.7	435.8	486.1	536.5	629.2	613.3	544.4	486.1	439.8	397.4	368.2
65°	290.1	357.6	397.4	441.1	515.3	521.9	466.3	425.2	382.8	345.7	319.2
67.5°	234.5	287.4	323.2	360.3	419.9	438.4	400.0	365.6	329.8	299.4	275.5
70°	189.4	226.5	253.0	282.1	331.2	353.7	333.8	310.0	280.8	255.6	234.5
72.5°	149.7	173.5	189.4	211.9	251.7	274.2	272.9	251.7	230.5	213.3	196.0
75°	109.9	128.5	141.7	156.3	188.1	209.3	214.6	205.3	184.1	170.9	157.6
77.5°	83.5	94.0	100.7	111.3	133.8	152.3	160.3	157.6	143.1	132.5	123.2
80°	63.6	66.2	68.9	72.9	91.4	108.6	113.9	112.6	104.6	100.7	90.1
82.5°	45.0	46.4	47.7	49.0	55.6	70.2	75.5	78.2	71.5	67.6	58.3
85°	26.5	27.8	27.8	30.5	31.8	35.8	45.0	45.0	43.7	38.4	37.1
87.5°	13.2	13.2	11.9	11.9	13.2	14.6	17.2	19.9	17.2	15.9	14.6
90°	19.8	14.9	13.4	11.9	9.9	7.9	4.0	1.0	4.0	7.9	9.9
92.5°	79.4	52.6	47.2	41.7	33.7	28.8	20.8	14.9	20.8	28.8	33.7
95°	142.9	97.3	85.4	73.4	57.6	48.6	38.7	34.7	38.7	48.6	57.6
97.5°	184.6	126.0	112.6	99.2	81.4	68.5	57.6	51.6	57.6	68.5	81.4
100°	204.4	151.8	137.9	124.0	104.2	88.3	79.4	76.4	79.4	88.3	104.2
102.5°	222.3	174.7	160.8	146.9	126.0	110.2	101.2	99.2	101.2	110.2	126.0
105°	243.1	196.5	182.6	168.7	146.9	132.0	125.0	121.1	125.0	132.0	146.9
107.5°	264.0	218.3	204.4	190.5	168.7	154.8	147.9	144.9	147.9	154.8	168.7
110°	284.8	241.1	226.8	212.4	191.5	178.6	172.7	168.7	172.7	178.6	191.5

TEST NUMBER: P1010378

CATALOG NUMBER: S122RDIP-B865D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	304.7	263.0	248.1	233.2	213.4	201.5	194.5	190.5	194.5	201.5	213.4
115°	325.5	282.8	269.4	256.0	236.2	224.3	218.3	213.4	218.3	224.3	236.2
117.5°	344.4	304.7	290.8	276.9	258.0	247.1	241.1	237.2	241.1	247.1	258.0
120°	364.2	325.5	311.6	297.7	277.9	268.9	263.0	259.0	263.0	268.9	277.9
122.5°	383.1	347.3	333.0	318.6	298.7	288.8	282.8	279.8	282.8	288.8	298.7
125°	401.9	366.2	352.3	338.4	318.6	306.6	300.7	297.7	300.7	306.6	318.6
127.5°	419.8	385.0	370.6	356.3	337.4	324.5	316.6	312.6	316.6	324.5	337.4
130°	435.7	400.9	387.0	373.1	353.3	339.4	329.5	325.5	329.5	339.4	353.3
132.5°	449.5	416.8	402.9	389.0	368.2	353.3	342.4	337.4	342.4	353.3	368.2
135°	462.4	430.7	416.8	402.9	380.1	365.2	353.3	349.3	353.3	365.2	380.1
137.5°	473.4	441.6	428.7	415.8	393.0	377.1	365.2	360.2	365.2	377.1	393.0
140°	482.3	452.5	439.6	426.7	404.9	389.0	377.1	373.1	377.1	389.0	404.9
142.5°	489.2	460.5	448.6	436.6	415.8	399.9	389.0	386.0	389.0	399.9	415.8
145°	496.2	469.4	458.5	447.6	427.7	412.8	402.9	398.9	402.9	412.8	427.7
147.5°	502.1	476.3	466.4	456.5	439.6	425.7	415.8	412.8	415.8	425.7	439.6
150°	506.1	483.3	474.4	465.4	450.5	437.6	429.7	426.7	429.7	437.6	450.5
152.5°	510.1	490.2	482.3	474.4	460.5	449.5	441.6	440.6	441.6	449.5	460.5
155°	514.1	497.2	489.8	482.3	471.4	460.5	454.5	453.5	454.5	460.5	471.4
157.5°	517.0	502.1	495.6	489.2	480.3	470.4	465.4	464.4	465.4	470.4	480.3
160°	519.0	507.1	501.6	496.2	488.2	480.3	476.3	475.3	476.3	480.3	488.2
162.5°	520.0	510.1	506.1	502.1	495.2	489.2	485.3	486.3	485.3	489.2	495.2
165°	521.0	512.1	509.1	506.1	501.1	495.2	493.2	494.2	493.2	495.2	501.1
167.5°	521.0	514.1	512.1	510.1	506.1	502.1	500.2	501.1	500.2	502.1	506.1
170°	520.0	515.0	513.6	512.1	510.1	507.1	506.1	508.1	506.1	507.1	510.1
172.5°	519.0	516.0	515.0	514.1	513.1	510.1	511.1	512.1	511.1	510.1	513.1
175°	518.0	516.0	515.5	515.0	515.0	513.1	514.1	515.0	514.1	513.1	515.0
177.5°	517.0	516.0	516.0	516.0	516.0	514.1	515.0	517.0	515.0	514.1	516.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P1010378

CATALOG NUMBER: S122RDIP-B865D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1884.9	1886.2	1890.2	1878.3	1859.8	1851.8	1828.0	1824.0	1820.0	1820.0	1824.0
5°	1842.5	1837.2	1838.6	1816.0	1789.5	1773.7	1740.5	1745.8	1728.6	1718.0	1720.7
7.5°	1796.2	1781.6	1780.3	1751.1	1718.0	1688.9	1654.4	1646.5	1630.6	1612.0	1604.1
10°	1737.9	1727.3	1707.4	1674.3	1631.9	1608.1	1561.7	1533.9	1529.9	1502.1	1491.5
12.5°	1678.3	1659.7	1639.9	1593.5	1545.8	1507.4	1473.0	1442.5	1421.3	1397.5	1381.6
15°	1609.4	1586.9	1564.4	1515.4	1459.7	1421.3	1369.6	1324.6	1262.4	1213.3	1185.5
17.5°	1533.9	1508.7	1478.3	1424.0	1369.6	1316.7	1221.3	1168.3	1124.6	1095.5	1078.2
20°	1455.7	1427.9	1397.5	1343.2	1249.1	1156.4	1103.4	1062.3	1035.8	1006.7	985.5
22.5°	1373.6	1344.5	1311.4	1226.6	1127.2	1062.3	1021.3	982.9	944.4	928.6	918.0
25°	1296.8	1270.3	1227.9	1112.7	1034.5	974.9	928.6	903.4	883.5	862.3	842.5
27.5°	1217.3	1168.3	1108.7	1012.0	963.0	902.1	868.9	850.4	816.0	801.4	792.1
30°	1121.9	1067.6	1010.7	941.8	884.8	842.5	812.0	781.5	761.7	747.1	731.2
32.5°	1025.2	973.6	937.8	866.3	823.9	780.2	751.1	732.5	703.4	694.1	687.5
35°	941.8	898.1	866.3	808.0	768.3	728.5	707.3	679.5	661.0	643.8	633.2
37.5°	859.7	835.8	802.7	753.7	711.3	679.5	650.4	641.1	615.9	606.7	596.1
40°	802.7	766.9	739.1	696.7	661.0	626.5	608.0	586.8	569.6	555.0	551.0
42.5°	733.8	707.3	691.4	645.1	608.0	588.1	565.6	541.8	528.5	516.6	502.0
45°	682.2	658.3	635.8	598.7	565.6	540.4	520.6	504.7	482.2	476.9	454.3
47.5°	627.9	604.0	586.8	549.7	519.2	495.4	480.8	459.6	441.1	429.2	418.6
50°	573.6	553.7	537.8	506.0	479.5	454.3	434.5	413.3	405.3	385.5	378.8
52.5°	521.9	508.7	491.4	461.0	434.5	413.3	392.1	374.9	362.9	352.3	344.4
55°	478.2	457.0	449.0	415.9	393.4	370.9	352.3	341.7	327.2	320.6	313.9
57.5°	429.2	417.3	404.0	378.8	353.7	332.5	319.2	303.3	295.4	287.4	282.1
60°	386.8	369.6	359.0	337.8	315.3	295.4	283.5	271.5	260.9	254.3	243.7
62.5°	337.8	324.5	317.9	295.4	276.8	258.3	247.7	235.8	227.8	215.9	202.7
65°	295.4	284.8	276.8	258.3	241.1	223.9	213.3	198.7	188.1	181.5	180.1
67.5°	258.3	250.4	238.4	221.2	204.0	190.7	178.8	166.9	165.6	162.9	162.9
70°	217.2	209.3	202.7	184.1	169.6	155.0	152.3	148.4	144.4	143.1	140.4
72.5°	181.5	174.8	166.9	151.0	136.4	132.5	129.8	127.2	123.2	121.9	120.5
75°	147.0	137.8	132.5	117.9	113.9	111.3	108.6	104.6	102.0	100.7	98.0
77.5°	112.6	103.3	103.3	95.4	92.7	88.7	86.1	83.5	82.1	79.5	79.5
80°	79.5	79.5	76.8	72.9	68.9	67.6	63.6	62.3	60.9	62.3	59.6
82.5°	58.3	53.0	53.0	50.3	47.7	46.4	43.7	43.7	42.4	42.4	42.4
85°	33.1	33.1	31.8	29.1	27.8	27.8	26.5	26.5	25.2	25.2	23.8
87.5°	13.2	11.9	13.2	11.9	11.9	10.6	10.6	10.6	9.3	10.6	9.3
90°	11.9	13.4	14.9	19.8	26.8	32.7	33.7	32.7	31.8	29.8	31.8
92.5°	41.7	47.2	52.6	79.4	117.1	150.8	152.8	128.0	100.2	85.3	74.4
95°	73.4	85.4	97.3	142.9	229.2	344.4	389.0	340.4	260.0	199.5	157.8
97.5°	99.2	112.6	126.0	184.6	304.7	490.2	634.1	639.1	531.9	424.7	324.5
100°	124.0	137.9	151.8	204.4	325.5	539.9	784.0	926.9	906.0	783.0	647.0
102.5°	146.9	160.8	174.7	222.3	326.5	521.0	788.9	1034.1	1151.2	1147.2	1056.9
105°	168.7	182.6	196.5	243.1	331.5	495.2	735.4	999.3	1205.7	1317.9	1330.8
107.5°	190.5	204.4	218.3	264.0	342.4	481.3	685.7	925.9	1147.2	1313.9	1411.2
110°	212.4	226.8	241.1	284.8	356.3	477.3	652.0	857.4	1066.8	1244.4	1371.5

TEST NUMBER: P1010378

CATALOG NUMBER: S122RDIP-B865D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	233.2	248.1	263.0	304.7	371.1	478.3	630.2	809.8	993.4	1162.1	1300.0
115°	256.0	269.4	282.8	325.5	386.0	482.3	615.3	772.1	935.8	1088.6	1218.6
117.5°	276.9	290.8	304.7	344.4	401.9	488.2	607.3	746.3	888.2	1025.1	1146.2
120°	297.7	311.6	325.5	364.2	417.8	494.2	600.4	726.4	854.4	977.5	1082.7
122.5°	318.6	333.0	347.3	383.1	431.7	501.1	596.4	709.5	827.6	937.8	1036.0
125°	338.4	352.3	366.2	401.9	446.6	508.1	591.5	693.7	801.8	904.1	991.4
127.5°	356.3	370.6	385.0	419.8	460.5	515.0	588.5	678.8	776.0	870.3	953.7
130°	373.1	387.0	400.9	435.7	473.4	523.0	586.5	663.9	751.2	836.6	915.0
132.5°	389.0	402.9	416.8	449.5	486.3	530.9	585.5	652.0	727.4	804.8	875.3
135°	402.9	416.8	430.7	462.4	497.2	536.9	584.5	641.1	705.6	771.1	836.6
137.5°	415.8	428.7	441.6	473.4	506.1	542.8	584.5	633.1	687.7	744.3	797.9
140°	426.7	439.6	452.5	482.3	513.1	546.8	583.5	626.2	670.8	718.5	764.1
142.5°	436.6	448.6	460.5	489.2	519.0	549.8	583.5	619.2	657.0	695.7	733.4
145°	447.6	458.5	469.4	496.2	524.0	551.8	581.5	613.3	644.1	676.8	707.6
147.5°	456.5	466.4	476.3	502.1	527.0	552.8	578.6	607.3	634.1	660.9	685.7
150°	465.4	474.4	483.3	506.1	528.9	551.8	575.6	599.4	623.2	645.0	665.9
152.5°	474.4	482.3	490.2	510.1	529.9	549.8	570.6	592.4	612.3	632.1	649.0
155°	482.3	489.8	497.2	514.1	530.9	547.8	564.7	583.5	602.4	618.2	633.1
157.5°	489.2	495.6	502.1	517.0	530.9	543.8	558.7	575.6	590.5	604.4	617.3
160°	496.2	501.6	507.1	519.0	530.9	540.8	552.8	566.6	579.5	590.5	601.4
162.5°	502.1	506.1	510.1	520.0	529.9	537.9	547.8	558.7	568.6	577.6	586.5
165°	506.1	509.1	512.1	521.0	527.9	533.9	540.8	549.8	557.7	564.7	571.6
167.5°	510.1	512.1	514.1	521.0	527.0	529.9	534.9	540.8	546.8	552.8	557.7
170°	512.1	513.6	515.0	520.0	525.0	527.0	529.9	533.9	538.9	541.8	545.8
172.5°	514.1	515.0	516.0	519.0	522.0	523.0	524.0	527.0	529.9	531.9	534.9
175°	515.0	515.5	516.0	518.0	520.0	519.0	520.0	521.0	524.0	525.0	526.0
177.5°	516.0	516.0	516.0	517.0	519.0	517.0	516.0	517.0	519.0	519.0	520.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P1010378

CATALOG NUMBER: S122RDIP-B865D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1824.0	1821.3	1813.4	1816.0	1812.1	1812.1	1809.4	1809.4	1809.4	1816.0	1812.1
5°	1724.6	1715.4	1706.1	1702.1	1698.1	1694.2	1694.2	1692.9	1704.8	1702.1	1712.7
7.5°	1601.5	1598.8	1580.3	1580.3	1573.6	1571.0	1577.6	1578.9	1580.3	1582.9	1589.5
10°	1491.5	1484.9	1458.4	1461.0	1457.1	1451.8	1455.7	1453.1	1462.4	1465.0	1462.4
12.5°	1361.7	1349.8	1320.6	1306.1	1290.2	1278.2	1292.8	1282.2	1319.3	1329.9	1359.0
15°	1189.5	1167.0	1147.1	1147.1	1132.5	1121.9	1128.6	1140.5	1148.4	1160.4	1165.7
17.5°	1074.3	1065.0	1049.1	1039.8	1035.8	1031.9	1031.9	1037.2	1054.4	1053.1	1063.7
20°	976.2	970.9	963.0	951.1	947.1	944.4	944.4	944.4	956.4	967.0	973.6
22.5°	908.7	904.7	899.4	883.5	875.6	872.9	879.5	883.5	892.8	900.7	907.4
25°	841.1	831.9	822.6	817.3	813.3	813.3	816.0	817.3	821.3	825.2	833.2
27.5°	785.5	778.9	765.6	751.1	751.1	747.1	749.7	752.4	761.7	774.9	781.5
30°	723.2	721.9	716.6	711.3	706.0	703.4	708.7	712.6	714.0	720.6	720.6
32.5°	678.2	668.9	659.7	654.4	651.7	650.4	651.7	657.0	657.0	665.0	674.2
35°	633.2	627.9	618.6	609.3	606.7	600.0	605.3	610.6	619.9	623.9	627.9
37.5°	584.2	577.5	573.6	570.9	565.6	566.9	563.0	570.9	578.9	577.5	580.2
40°	547.1	535.1	523.2	521.9	520.6	519.2	519.2	520.6	525.9	531.2	539.1
42.5°	499.4	495.4	484.8	474.2	471.6	468.9	466.3	471.6	482.2	491.4	495.4
45°	450.4	445.1	442.4	434.5	429.2	427.8	425.2	431.8	441.1	445.1	447.7
47.5°	405.3	404.0	396.1	397.4	393.4	394.7	393.4	397.4	397.4	401.4	404.0
50°	374.9	370.9	366.9	364.3	360.3	360.3	359.0	360.3	365.6	370.9	369.6
52.5°	344.4	337.8	336.5	335.1	332.5	335.1	331.2	332.5	337.8	340.4	339.1
55°	308.6	307.3	304.7	302.0	300.7	299.4	299.4	299.4	304.7	308.6	310.0
57.5°	280.8	274.2	268.9	268.9	263.6	262.3	264.9	266.2	270.2	272.9	275.5
60°	242.4	239.8	231.8	227.8	219.9	218.6	218.6	223.9	230.5	239.8	242.4
62.5°	201.3	197.4	196.0	196.0	196.0	196.0	196.0	196.0	196.0	197.4	197.4
65°	178.8	180.1	178.8	177.5	178.8	178.8	177.5	177.5	177.5	178.8	180.1
67.5°	160.3	159.0	160.3	159.0	157.6	157.6	156.3	157.6	159.0	160.3	160.3
70°	139.1	139.1	137.8	139.1	137.8	136.4	135.1	135.1	137.8	139.1	139.1
72.5°	119.2	119.2	117.9	117.9	115.2	115.2	116.6	115.2	115.2	119.2	119.2
75°	99.3	98.0	96.7	96.7	95.4	95.4	95.4	94.0	96.7	96.7	98.0
77.5°	78.2	78.2	78.2	76.8	76.8	75.5	75.5	76.8	76.8	76.8	78.2
80°	59.6	59.6	59.6	58.3	57.0	57.0	57.0	57.0	57.0	58.3	57.0
82.5°	41.1	41.1	41.1	41.1	41.1	39.7	39.7	39.7	41.1	41.1	39.7
85°	25.2	23.8	25.2	25.2	23.8	25.2	23.8	23.8	22.5	22.5	23.8
87.5°	10.6	9.3	7.9	7.9	9.3	7.9	7.9	7.9	9.3	7.9	7.9
90°	32.2	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.2
92.5°	70.4	66.5	65.5	61.5	62.5	60.5	62.5	61.5	65.5	66.5	70.4
95°	146.9	136.0	123.1	115.1	112.1	113.1	112.1	115.1	123.1	136.0	146.9
97.5°	294.8	265.0	226.3	206.4	195.5	189.5	195.5	206.4	226.3	265.0	294.8
100°	587.0	527.0	444.6	401.9	373.1	355.3	373.1	401.9	444.6	527.0	587.0
102.5°	992.4	927.9	836.6	756.2	718.5	692.7	718.5	756.2	836.6	927.9	992.4
105°	1314.4	1298.0	1236.5	1175.0	1132.3	1118.4	1132.3	1175.0	1236.5	1298.0	1314.4
107.5°	1431.1	1450.9	1449.9	1440.9	1428.0	1405.2	1428.0	1440.9	1449.9	1450.9	1431.1
110°	1412.2	1452.8	1495.5	1514.4	1523.3	1522.3	1523.3	1514.4	1495.5	1452.8	1412.2

TEST NUMBER: P1010378

CATALOG NUMBER: S122RDIP-B865D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1348.2	1396.3	1459.8	1494.5	1513.4	1520.3	1513.4	1494.5	1459.8	1396.3	1348.2
115°	1269.8	1320.9	1391.3	1437.0	1462.8	1471.7	1462.8	1437.0	1391.3	1320.9	1269.8
117.5°	1194.8	1243.4	1315.9	1364.5	1391.3	1398.3	1391.3	1364.5	1315.9	1243.4	1194.8
120°	1127.8	1173.0	1242.5	1289.1	1317.9	1327.8	1317.9	1289.1	1242.5	1173.0	1127.8
122.5°	1075.7	1115.4	1176.0	1221.6	1246.4	1254.4	1246.4	1221.6	1176.0	1115.4	1075.7
125°	1028.6	1065.8	1123.4	1161.1	1185.9	1193.8	1185.9	1161.1	1123.4	1065.8	1028.6
127.5°	988.4	1023.1	1073.8	1109.5	1131.3	1137.3	1131.3	1109.5	1073.8	1023.1	988.4
130°	947.8	980.5	1029.1	1062.8	1082.7	1090.6	1082.7	1062.8	1029.1	980.5	947.8
132.5°	905.6	935.8	983.4	1017.2	1035.0	1042.0	1035.0	1017.2	983.4	935.8	905.6
135°	864.4	892.1	934.8	967.6	985.4	989.4	985.4	967.6	934.8	892.1	864.4
137.5°	822.7	847.5	888.2	917.0	932.8	938.8	932.8	917.0	888.2	847.5	822.7
140°	786.0	807.8	839.5	865.4	880.2	886.2	880.2	865.4	839.5	807.8	786.0
142.5°	750.8	768.1	797.9	820.7	833.6	833.6	833.6	820.7	797.9	768.1	750.8
145°	722.0	736.3	760.2	777.0	787.0	789.9	787.0	777.0	760.2	736.3	722.0
147.5°	696.7	707.6	728.4	742.3	749.2	751.2	749.2	742.3	728.4	707.6	696.7
150°	674.8	683.7	698.6	710.5	716.5	717.5	716.5	710.5	698.6	683.7	674.8
152.5°	656.4	663.9	674.8	684.7	688.7	688.7	688.7	684.7	674.8	663.9	656.4
155°	638.6	644.1	655.0	661.9	665.9	663.9	665.9	661.9	655.0	644.1	638.6
157.5°	621.8	626.2	634.1	640.1	642.1	642.1	642.1	640.1	634.1	626.2	621.8
160°	604.8	608.3	615.3	620.2	621.2	621.2	621.2	620.2	615.3	608.3	604.8
162.5°	589.0	591.5	598.4	601.4	602.4	601.4	602.4	601.4	598.4	591.5	589.0
165°	573.6	575.6	579.5	583.5	583.5	582.5	583.5	583.5	579.5	575.6	573.6
167.5°	559.7	561.7	563.7	565.7	565.7	564.7	565.7	565.7	563.7	561.7	559.7
170°	546.8	547.8	548.8	551.8	550.8	548.8	550.8	551.8	548.8	547.8	546.8
172.5°	535.4	535.9	536.9	537.9	536.9	535.9	536.9	537.9	536.9	535.9	535.4
175°	526.5	527.0	527.0	527.9	527.0	525.0	527.0	527.9	527.0	527.0	526.5
177.5°	520.0	520.0	520.0	520.0	519.0	517.0	519.0	520.0	520.0	520.0	520.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P1010378

CATALOG NUMBER: S122RDIP-B865D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1816.0	1822.7	1820.0	1805.4	1820.0	1824.0	1831.9	1839.9	1845.2	1853.1	1859.8
5°	1702.1	1715.4	1723.3	1715.4	1741.9	1745.8	1764.4	1775.0	1790.9	1804.1	1814.7
7.5°	1594.8	1605.4	1621.3	1624.0	1639.9	1658.4	1684.9	1711.4	1736.6	1749.8	1761.7
10°	1479.6	1498.1	1522.0	1516.7	1540.5	1569.7	1597.5	1639.9	1661.1	1684.9	1706.1
12.5°	1364.3	1376.3	1408.1	1418.7	1453.1	1475.6	1514.0	1540.5	1593.5	1621.3	1639.9
15°	1163.0	1212.0	1251.8	1299.4	1344.5	1386.9	1421.3	1469.0	1515.4	1536.5	1567.0
17.5°	1071.6	1094.1	1118.0	1141.8	1200.1	1275.6	1336.5	1388.2	1427.9	1455.7	1491.5
20°	976.2	998.8	1025.2	1047.8	1083.5	1137.8	1213.3	1302.1	1349.8	1378.9	1413.4
22.5°	908.7	929.9	947.1	967.0	994.8	1034.5	1091.5	1201.4	1265.0	1300.8	1331.2
25°	835.8	862.3	880.9	895.4	918.0	961.7	1008.0	1070.3	1184.2	1212.0	1254.4
27.5°	785.5	793.4	814.6	837.2	859.7	883.5	931.2	984.2	1061.0	1121.9	1173.6
30°	725.9	745.8	765.6	774.9	794.8	829.2	858.3	915.3	974.9	1022.6	1084.9
32.5°	680.8	692.8	706.0	728.5	747.1	770.9	800.1	847.8	898.1	928.6	976.2
35°	630.5	638.5	666.3	675.6	694.1	717.9	747.1	784.2	838.5	862.3	896.8
37.5°	582.8	601.4	609.3	630.5	647.7	671.6	692.8	735.2	770.9	798.7	830.5
40°	545.7	553.7	568.3	586.8	601.4	619.9	646.4	676.9	715.3	737.8	765.6
42.5°	500.7	507.3	525.9	536.5	560.3	577.5	593.4	630.5	665.0	682.2	710.0
45°	451.7	467.6	479.5	500.7	513.9	535.1	555.0	581.5	613.3	633.2	649.1
47.5°	409.3	425.2	437.1	457.0	478.2	487.5	508.7	536.5	565.6	581.5	604.0
50°	374.9	380.2	402.7	412.0	434.5	453.0	467.6	491.4	523.2	532.5	551.0
52.5°	341.7	345.7	360.3	372.2	392.1	408.0	426.5	449.0	475.5	490.1	504.7
55°	312.6	315.3	321.9	335.1	348.4	368.2	385.5	406.7	429.2	445.1	458.3
57.5°	279.5	284.8	290.1	298.0	311.3	329.8	348.4	368.2	386.8	397.4	414.6
60°	241.1	249.0	258.3	267.6	276.8	290.1	311.3	329.8	347.0	356.3	369.6
62.5°	200.0	215.9	223.9	234.5	242.4	254.3	270.2	291.4	303.3	315.3	325.9
65°	180.1	181.5	182.8	193.4	208.0	219.9	234.5	250.4	268.9	276.8	284.8
67.5°	160.3	161.6	164.3	165.6	170.9	184.1	200.0	217.2	231.8	237.1	245.1
70°	140.4	140.4	145.7	147.0	148.4	149.7	162.9	180.1	193.4	200.0	209.3
72.5°	119.2	120.5	123.2	124.5	127.2	129.8	133.8	143.1	159.0	165.6	176.2
75°	98.0	99.3	100.7	102.0	106.0	107.3	111.3	116.6	123.2	131.1	137.8
77.5°	78.2	78.2	79.5	82.1	84.8	86.1	90.1	92.7	95.4	99.3	104.6
80°	58.3	59.6	59.6	62.3	62.3	63.6	64.9	68.9	71.5	74.2	76.8
82.5°	39.7	42.4	42.4	42.4	43.7	45.0	46.4	46.4	49.0	50.3	54.3
85°	23.8	25.2	25.2	25.2	23.8	26.5	26.5	27.8	27.8	27.8	29.1
87.5°	9.3	7.9	9.3	9.3	9.3	10.6	9.3	9.3	10.6	11.9	11.9
90°	31.8	29.8	31.8	32.7	33.7	32.7	26.8	19.8	14.9	13.4	11.9
92.5°	74.4	85.3	100.2	128.0	152.8	150.8	117.1	79.4	52.6	47.2	41.7
95°	157.8	199.5	260.0	340.4	389.0	344.4	229.2	142.9	97.3	85.4	73.4
97.5°	324.5	424.7	531.9	639.1	634.1	490.2	304.7	184.6	126.0	112.6	99.2
100°	647.0	783.0	906.0	926.9	784.0	539.9	325.5	204.4	151.8	137.9	124.0
102.5°	1056.9	1147.2	1151.2	1034.1	788.9	521.0	326.5	222.3	174.7	160.8	146.9
105°	1330.8	1317.9	1205.7	999.3	735.4	495.2	331.5	243.1	196.5	182.6	168.7
107.5°	1411.2	1313.9	1147.2	925.9	685.7	481.3	342.4	264.0	218.3	204.4	190.5
110°	1371.5	1244.4	1066.8	857.4	652.0	477.3	356.3	284.8	241.1	226.8	212.4

TEST NUMBER: P1010378

CATALOG NUMBER: S122RDIP-B865D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1300.0	1162.1	993.4	809.8	630.2	478.3	371.1	304.7	263.0	248.1	233.2
115°	1218.6	1088.6	935.8	772.1	615.3	482.3	386.0	325.5	282.8	269.4	256.0
117.5°	1146.2	1025.1	888.2	746.3	607.3	488.2	401.9	344.4	304.7	290.8	276.9
120°	1082.7	977.5	854.4	726.4	600.4	494.2	417.8	364.2	325.5	311.6	297.7
122.5°	1036.0	937.8	827.6	709.5	596.4	501.1	431.7	383.1	347.3	333.0	318.6
125°	991.4	904.1	801.8	693.7	591.5	508.1	446.6	401.9	366.2	352.3	338.4
127.5°	953.7	870.3	776.0	678.8	588.5	515.0	460.5	419.8	385.0	370.6	356.3
130°	915.0	836.6	751.2	663.9	586.5	523.0	473.4	435.7	400.9	387.0	373.1
132.5°	875.3	804.8	727.4	652.0	585.5	530.9	486.3	449.5	416.8	402.9	389.0
135°	836.6	771.1	705.6	641.1	584.5	536.9	497.2	462.4	430.7	416.8	402.9
137.5°	797.9	744.3	687.7	633.1	584.5	542.8	506.1	473.4	441.6	428.7	415.8
140°	764.1	718.5	670.8	626.2	583.5	546.8	513.1	482.3	452.5	439.6	426.7
142.5°	733.4	695.7	657.0	619.2	583.5	549.8	519.0	489.2	460.5	448.6	436.6
145°	707.6	676.8	644.1	613.3	581.5	551.8	524.0	496.2	469.4	458.5	447.6
147.5°	685.7	660.9	634.1	607.3	578.6	552.8	527.0	502.1	476.3	466.4	456.5
150°	665.9	645.0	623.2	599.4	575.6	551.8	528.9	506.1	483.3	474.4	465.4
152.5°	649.0	632.1	612.3	592.4	570.6	549.8	529.9	510.1	490.2	482.3	474.4
155°	633.1	618.2	602.4	583.5	564.7	547.8	530.9	514.1	497.2	489.8	482.3
157.5°	617.3	604.4	590.5	575.6	558.7	543.8	530.9	517.0	502.1	495.6	489.2
160°	601.4	590.5	579.5	566.6	552.8	540.8	530.9	519.0	507.1	501.6	496.2
162.5°	586.5	577.6	568.6	558.7	547.8	537.9	529.9	520.0	510.1	506.1	502.1
165°	571.6	564.7	557.7	549.8	540.8	533.9	527.9	521.0	512.1	509.1	506.1
167.5°	557.7	552.8	546.8	540.8	534.9	529.9	527.0	521.0	514.1	512.1	510.1
170°	545.8	541.8	538.9	533.9	529.9	527.0	525.0	520.0	515.0	513.6	512.1
172.5°	534.9	531.9	529.9	527.0	524.0	523.0	522.0	519.0	516.0	515.0	514.1
175°	526.0	525.0	524.0	521.0	520.0	519.0	520.0	518.0	516.0	515.5	515.0
177.5°	520.0	519.0	519.0	517.0	516.0	517.0	519.0	517.0	516.0	516.0	516.0
180°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0

TEST NUMBER: P1010378

CATALOG NUMBER: S122RDIP-B865D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1906.1	1906.1	1906.1	1906.1
2.5°	1871.7	1867.7	1891.5	1918.0
5°	1833.3	1839.9	1870.3	1907.4
7.5°	1793.5	1808.1	1843.9	1892.9
10°	1737.9	1764.4	1818.7	1869.0
12.5°	1683.6	1719.3	1771.0	1830.6
15°	1622.6	1662.4	1726.0	1797.5
17.5°	1555.1	1600.1	1674.3	1752.5
20°	1483.6	1543.2	1621.3	1706.1
22.5°	1404.1	1475.6	1556.4	1650.5
25°	1327.3	1405.4	1486.2	1594.8
27.5°	1251.8	1328.6	1418.7	1528.6
30°	1176.3	1246.5	1343.2	1461.0
32.5°	1095.5	1168.3	1270.3	1390.8
35°	1021.3	1094.1	1189.5	1308.7
37.5°	941.8	1019.9	1111.3	1234.5
40°	849.1	940.5	1029.2	1147.1
42.5°	772.2	868.9	955.0	1066.3
45°	711.3	802.7	874.2	982.9
47.5°	654.4	728.5	801.4	902.1
50°	600.0	657.0	732.5	822.6
52.5°	544.4	593.4	658.3	743.1
55°	494.1	540.4	598.7	663.6
57.5°	447.7	480.8	539.1	597.4
60°	396.1	430.5	475.5	524.5
62.5°	352.3	378.8	421.2	462.3
65°	306.0	331.2	362.9	401.4
67.5°	263.6	286.1	311.3	341.7
70°	225.2	242.4	260.9	287.4
72.5°	184.1	202.7	219.9	241.1
75°	151.0	159.0	173.5	188.1
77.5°	116.6	127.2	135.1	147.0
80°	83.5	92.7	95.4	104.6
82.5°	55.6	60.9	66.2	68.9
85°	31.8	34.4	39.7	41.1
87.5°	11.9	13.2	15.9	18.5
90°	9.9	7.9	4.0	1.0
92.5°	33.7	28.8	20.8	14.9
95°	57.6	48.6	38.7	34.7
97.5°	81.4	68.5	57.6	51.6
100°	104.2	88.3	79.4	76.4
102.5°	126.0	110.2	101.2	99.2
105°	146.9	132.0	125.0	121.1
107.5°	168.7	154.8	147.9	144.9
110°	191.5	178.6	172.7	168.7

TEST NUMBER: P1010378

CATALOG NUMBER: S122RDIP-B865D925UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	213.4	201.5	194.5	190.5
115°	236.2	224.3	218.3	213.4
117.5°	258.0	247.1	241.1	237.2
120°	277.9	268.9	263.0	259.0
122.5°	298.7	288.8	282.8	279.8
125°	318.6	306.6	300.7	297.7
127.5°	337.4	324.5	316.6	312.6
130°	353.3	339.4	329.5	325.5
132.5°	368.2	353.3	342.4	337.4
135°	380.1	365.2	353.3	349.3
137.5°	393.0	377.1	365.2	360.2
140°	404.9	389.0	377.1	373.1
142.5°	415.8	399.9	389.0	386.0
145°	427.7	412.8	402.9	398.9
147.5°	439.6	425.7	415.8	412.8
150°	450.5	437.6	429.7	426.7
152.5°	460.5	449.5	441.6	440.6
155°	471.4	460.5	454.5	453.5
157.5°	480.3	470.4	465.4	464.4
160°	488.2	480.3	476.3	475.3
162.5°	495.2	489.2	485.3	486.3
165°	501.1	495.2	493.2	494.2
167.5°	506.1	502.1	500.2	501.1
170°	510.1	507.1	506.1	508.1
172.5°	513.1	510.1	511.1	512.1
175°	515.0	513.1	514.1	515.0
177.5°	516.0	514.1	515.0	517.0
180°	516.0	516.0	516.0	516.0

(END OF REPORT)