

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010636

Luminaire Tested: S123DIP-B560D1195UB2750-4F0-XX-W2A-A_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010636
REPORT IS A COMBINATION OF REPORTS P989990 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D1195UB2750-4F0-XX-W2A-A_3500K
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7174.0 lumens
Efficiency: N/A
Efficacy: 121.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010636

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010636

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41			33
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	36	35			28
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30			24
3	78	69	62	57	70	63	57	52	51	46	43	39	36	34	29	27	25			21
4	72	61	54	48	64	56	49	44	45	40	36	35	32	29	26	24	22			18
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19			16
6	61	49	41	36	54	45	38	33	36	31	27	28	25	22	21	19	17			14
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15			12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	18	15	13			11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12			10
10	45	33	26	22	41	30	24	20	25	20	17	20	16	14	15	13	11			9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8509	8509	8509	8509
5°	8515	9805	8540	7317
10°	8461	11865	8469	6390
15°	8344	14071	8412	5752
20°	8243	16200	8260	5292
25°	8093	16608	8112	5053
30°	7987	13721	7987	4896
35°	7854	9177	7805	4758
40°	7696	6625	7601	4545
45°	7497	5247	7282	4281
50°	7013	4457	6765	4022
55°	6481	3916	6219	3732
60°	5943	3409	5627	3429
65°	5352	2920	5093	3024
70°	4738	2423	4420	2550
75°	4051	1827	3789	1969
80°	3203	1219	2953	1293
85°	2209	561	1767	510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 13723 cd/sqm

TEST NUMBER: P1010636

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.7	1.1
10°-20°	249.7	3.5
20°-30°	420.2	5.9
30°-40°	474.8	6.6
40°-50°	425.3	5.9
50°-60°	343.3	4.8
60°-70°	239.2	3.3
70°-80°	125.6	1.8
80°-90°	33.2	0.5
90°-100°	55.3	0.8
100°-110°	267.6	3.7
110°-120°	655.8	9.1
120°-130°	832.5	11.6
130°-140°	889.3	12.4
140°-150°	831.6	11.6
150°-160°	670.8	9.3
160°-170°	432.9	6.0
170°-180°	149.2	2.1
0°-30°	747.6	10.4
0°-40°	1222.5	17.0
0°-60°	1991.1	27.8
0°-90°	2389.1	33.3
90°-120°	978.7	13.6
90°-150°	3532.1	49.2
90°-180°	4785.0	66.7
0°-180°	7174.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	790	790	790	790	790	
5°	790	939	792	701	790	75
15°	754	1398	760	572	754	213
25°	689	1659	691	505	689	318
35°	608	894	604	464	608	381
45°	505	483	490	394	505	386
55°	358	328	343	312	358	320
65°	221	213	211	221	221	220
75°	106	110	100	118	106	114
85°	23	25	18	23	23	26
90°	1	35	1	35	1	6
95°	71	44	71	44	71	85
105°	348	51	348	51	348	368
115°	652	686	652	686	652	644
125°	919	938	919	938	919	821
135°	1144	1156	1144	1156	1144	881
145°	1320	1333	1320	1333	1320	826
155°	1454	1452	1454	1452	1454	670
165°	1533	1530	1533	1530	1533	433
175°	1570	1564	1570	1564	1570	149
180°	1570	1570	1570	1570	1570	

TEST NUMBER: P1010636

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	792.8	799.0	802.0	806.6	811.2	818.1	820.4	824.3	822.7	825.8	827.3
5°	789.8	800.5	809.7	821.2	831.9	839.6	847.2	859.5	868.7	870.2	877.1
7.5°	784.4	799.7	815.8	831.9	852.6	864.9	878.6	895.5	909.3	931.5	939.9
10°	777.5	799.0	822.0	844.2	872.5	891.7	908.5	936.9	965.2	988.2	1009.6
12.5°	766.8	793.6	823.5	856.4	893.2	915.4	938.4	975.9	1018.8	1054.1	1077.0
15°	753.8	787.5	825.8	861.0	901.6	943.0	967.5	1009.6	1070.9	1103.9	1162.8
17.5°	743.1	777.5	815.8	871.0	926.1	967.5	985.1	1062.5	1104.6	1159.8	1226.4
20°	726.2	769.9	818.9	874.0	945.3	970.6	1006.6	1084.7	1136.8	1208.8	1290.8
22.5°	708.6	755.3	814.3	871.7	951.4	978.2	1027.3	1089.3	1172.0	1243.3	1333.7
25°	689.4	740.0	799.7	867.9	946.1	985.1	1031.1	1107.7	1197.3	1286.9	1370.4
27.5°	670.3	725.4	787.5	855.7	931.5	977.5	1023.4	1103.1	1218.0	1315.3	1421.8
30°	651.9	707.0	769.1	838.8	918.5	962.9	1006.6	1106.2	1234.1	1343.6	1450.9
32.5°	632.0	688.7	753.8	812.0	892.4	939.9	989.0	1106.2	1244.0	1360.5	1458.5
35°	608.2	666.5	722.4	780.6	860.3	913.1	968.3	1098.5	1253.2	1365.8	1426.4
37.5°	585.3	636.6	684.8	741.5	825.0	881.7	945.3	1089.3	1248.6	1342.9	1359.7
40°	559.2	610.5	649.6	702.5	790.5	856.4	920.8	1077.0	1228.7	1288.5	1239.4
42.5°	533.9	574.5	608.2	659.6	755.3	819.7	889.4	1054.8	1189.7	1201.9	1091.6
45°	504.8	533.9	563.8	622.0	717.0	782.9	860.3	1022.7	1126.8	1091.6	952.2
47.5°	467.3	493.3	526.3	579.9	676.4	744.6	818.1	981.3	1035.7	962.1	809.7
50°	431.3	453.5	484.1	536.2	633.5	700.2	778.3	916.2	943.0	827.3	697.9
52.5°	395.3	412.1	442.0	494.1	591.4	655.7	727.0	849.5	834.2	710.1	595.2
55°	357.7	372.3	400.6	452.0	542.4	603.6	671.8	767.6	727.7	609.8	517.8
57.5°	321.0	336.3	365.4	408.3	493.3	553.1	607.5	682.5	622.8	528.6	447.4
60°	288.0	301.1	323.3	365.4	442.8	491.0	540.8	592.1	542.4	451.2	389.1
62.5°	253.6	265.8	286.5	324.8	391.4	434.3	474.2	516.3	461.2	394.5	339.4
65°	221.4	231.3	250.5	285.7	340.1	375.4	407.5	436.6	392.2	330.9	289.6
67.5°	192.3	200.7	216.8	248.2	294.2	319.4	345.5	370.0	332.5	283.4	248.2
70°	160.9	167.8	182.3	205.3	242.1	268.1	287.3	305.6	271.9	232.9	209.1
72.5°	133.3	140.2	149.4	173.1	198.4	214.5	235.2	245.1	226.0	193.8	170.1
75°	106.5	111.8	120.3	135.6	159.3	170.1	183.1	190.7	173.1	151.7	137.1
77.5°	83.5	85.8	91.9	102.6	118.7	131.0	141.0	145.5	133.3	119.5	107.2
80°	59.0	62.0	66.6	75.8	88.1	91.9	98.1	103.4	95.8	83.5	75.8
82.5°	39.1	42.9	45.2	49.0	56.7	61.3	62.8	67.4	60.5	55.9	52.9
85°	23.0	24.5	25.3	27.6	31.4	33.7	36.0	36.8	35.2	34.5	31.4
87.5°	11.5	11.5	11.5	13.0	13.8	15.3	16.1	16.1	16.1	15.3	14.6
90°	1.2	3.8	6.4	8.9	11.5	12.8	14.5	17.9	21.2	24.6	28.0
92.5°	26.8	25.2	23.7	22.1	20.6	19.8	21.0	23.3	25.6	28.0	30.3
95°	71.1	60.5	49.9	39.2	28.6	23.3	24.7	27.6	30.4	33.3	36.1
97.5°	129.4	122.2	114.9	107.7	100.4	96.8	90.2	77.0	63.7	50.5	37.3
100°	197.1	202.3	207.5	212.6	217.8	220.4	200.2	159.8	119.3	78.9	38.5
102.5°	274.0	277.4	280.8	284.1	287.5	289.2	266.7	221.6	176.5	131.4	86.3
105°	347.5	350.3	353.2	356.0	358.9	360.3	348.6	325.3	302.0	278.7	255.4
107.5°	425.6	427.9	430.3	432.6	434.9	436.1	438.0	441.9	445.8	449.7	453.6
110°	503.7	505.8	507.9	510.0	512.1	513.1	514.5	517.4	520.2	523.1	525.9

TEST NUMBER: P1010636

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	578.4	580.2	582.0	583.8	585.6	586.5	587.9	590.8	593.7	596.5	599.4
115°	651.8	653.4	654.9	656.5	658.0	658.8	660.0	662.3	664.6	667.0	669.3
117.5°	724.1	725.9	727.7	729.6	731.4	732.3	732.9	734.2	735.5	736.8	738.1
120°	790.6	792.9	795.3	797.6	799.9	801.1	801.5	802.3	803.0	803.8	804.6
122.5°	858.2	860.0	861.8	863.7	865.5	866.4	866.9	868.0	869.0	870.1	871.1
125°	918.9	921.0	923.0	925.1	927.2	928.2	928.7	929.8	930.8	931.9	932.9
127.5°	979.5	981.6	983.6	985.7	987.8	988.8	989.5	990.8	992.1	993.4	994.7
130°	1035.5	1037.6	1039.6	1041.7	1043.8	1044.8	1045.3	1046.4	1047.4	1048.5	1049.5
132.5°	1089.1	1091.2	1093.2	1095.3	1097.4	1098.4	1098.8	1099.6	1100.3	1101.1	1101.9
135°	1143.9	1145.5	1147.0	1148.6	1150.1	1150.9	1151.4	1152.5	1153.5	1154.6	1155.6
137.5°	1190.6	1192.7	1194.7	1196.8	1198.9	1199.9	1200.2	1200.7	1201.2	1201.7	1202.2
140°	1237.2	1238.8	1240.3	1241.9	1243.4	1244.2	1244.6	1245.4	1246.1	1246.9	1247.7
142.5°	1280.4	1281.9	1283.5	1285.0	1286.5	1287.3	1287.7	1288.5	1289.2	1290.0	1290.8
145°	1320.0	1321.8	1323.6	1325.5	1327.3	1328.2	1328.5	1329.0	1329.5	1330.0	1330.5
147.5°	1358.5	1359.8	1361.1	1362.4	1363.7	1364.3	1364.6	1365.1	1365.6	1366.1	1366.6
150°	1393.5	1394.3	1395.1	1395.8	1396.6	1397.0	1397.3	1397.8	1398.3	1398.8	1399.3
152.5°	1424.9	1425.2	1425.4	1425.7	1426.0	1426.1	1426.2	1426.5	1426.8	1427.0	1427.3
155°	1454.1	1453.6	1453.1	1452.6	1452.1	1451.8	1451.9	1452.2	1452.4	1452.7	1452.9
157.5°	1477.4	1477.4	1477.4	1477.4	1477.4	1477.4	1477.3	1477.0	1476.8	1476.5	1476.3
160°	1498.4	1498.1	1497.9	1497.6	1497.3	1497.2	1497.1	1496.8	1496.6	1496.3	1496.1
162.5°	1518.2	1517.4	1516.6	1515.9	1515.1	1514.7	1514.6	1514.3	1514.1	1513.8	1513.6
165°	1533.4	1532.6	1531.8	1531.1	1530.3	1529.9	1529.8	1529.5	1529.2	1529.0	1528.7
167.5°	1546.2	1545.2	1544.2	1543.1	1542.1	1541.6	1541.6	1541.6	1541.6	1541.6	1541.6
170°	1556.7	1555.7	1554.6	1553.6	1552.5	1552.0	1552.0	1552.0	1552.0	1552.0	1552.0
172.5°	1563.7	1562.4	1561.1	1559.8	1558.5	1557.9	1558.0	1558.3	1558.5	1558.8	1559.0
175°	1569.5	1568.2	1566.9	1565.6	1564.3	1563.7	1563.8	1564.1	1564.4	1564.6	1564.9
177.5°	1571.9	1570.6	1569.3	1568.0	1566.7	1566.0	1566.1	1566.4	1566.7	1566.9	1567.2
180°	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5

TEST NUMBER: P1010636

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	832.7	834.2	839.6	843.4	851.1	850.3	850.3	849.5	847.2	851.1	853.4
5°	890.9	903.9	905.5	922.3	923.1	930.0	934.6	930.7	939.9	939.2	932.3
7.5°	962.9	980.5	989.0	1005.0	1023.4	1018.8	1036.4	1039.5	1038.0	1045.6	1051.0
10°	1041.8	1072.4	1093.9	1123.8	1131.4	1136.0	1147.5	1157.5	1177.4	1162.1	1172.0
12.5°	1132.2	1154.4	1182.8	1230.3	1254.0	1269.3	1274.7	1281.6	1295.4	1286.9	1287.7
15°	1208.0	1237.9	1286.2	1345.2	1352.1	1371.2	1366.6	1408.0	1427.9	1398.0	1414.9
17.5°	1286.9	1326.8	1384.2	1435.5	1464.7	1477.7	1489.9	1529.8	1528.2	1523.6	1527.5
20°	1337.5	1402.6	1473.9	1542.0	1550.5	1560.4	1593.4	1610.2	1607.1	1620.2	1628.6
22.5°	1408.7	1477.7	1553.5	1598.7	1617.9	1629.4	1655.4	1666.1	1670.7	1673.8	1668.4
25°	1468.5	1542.0	1597.9	1637.8	1649.3	1655.4	1663.8	1666.9	1664.6	1659.2	1663.8
27.5°	1509.1	1568.1	1606.4	1624.8	1618.6	1608.7	1592.6	1581.9	1558.1	1546.6	1560.4
30°	1525.9	1552.0	1563.5	1532.8	1502.2	1477.7	1447.0	1390.4	1345.9	1358.9	1341.3
32.5°	1499.1	1482.3	1427.1	1348.2	1324.5	1284.6	1198.1	1131.4	1133.7	1098.5	1113.0
35°	1420.2	1343.6	1239.4	1119.9	1088.5	1067.1	972.1	957.5	926.9	894.0	903.2
37.5°	1280.8	1169.0	1042.6	954.5	907.8	861.0	807.4	775.2	756.8	743.1	753.8
40°	1110.8	974.4	870.2	791.3	751.5	721.6	684.8	652.7	632.0	629.7	633.5
42.5°	943.8	828.8	733.1	658.0	645.0	609.8	586.0	560.7	554.6	544.7	550.0
45°	799.0	705.5	626.6	565.3	550.0	540.8	511.7	495.6	488.7	482.6	491.8
47.5°	694.0	596.0	538.5	501.8	486.4	471.1	455.0	444.3	438.9	439.7	438.9
50°	592.9	520.9	470.3	442.0	432.8	422.1	409.1	402.2	399.9	393.0	398.3
52.5°	510.2	458.1	422.9	396.0	389.1	381.5	370.8	366.9	361.6	360.0	360.0
55°	443.5	402.9	374.6	357.0	348.5	342.4	336.3	331.7	327.9	327.9	327.9
57.5°	391.4	356.2	335.5	320.2	317.1	311.0	304.1	304.1	298.8	298.0	300.3
60°	347.0	315.6	299.5	286.5	281.9	280.4	273.5	273.5	271.9	268.1	271.2
62.5°	301.8	278.8	265.0	255.1	250.5	250.5	245.1	241.3	241.3	242.1	240.5
65°	260.5	243.6	231.3	223.7	221.4	218.3	217.6	214.5	212.2	213.0	212.2
67.5°	223.7	210.7	202.2	196.1	192.3	190.7	188.4	188.4	186.9	187.7	183.8
70°	190.7	177.7	170.8	164.7	163.2	163.2	160.1	160.9	159.3	161.6	160.1
72.5°	157.0	147.1	141.7	139.4	137.9	137.1	135.6	134.1	133.3	134.8	134.1
75°	127.2	118.7	114.9	113.4	111.8	111.8	111.1	110.3	109.5	109.5	109.5
77.5°	98.8	93.5	88.9	90.4	88.1	88.9	86.6	86.6	87.3	86.6	86.6
80°	72.8	68.9	68.9	67.4	64.3	65.9	65.9	63.6	62.8	64.3	62.0
82.5°	48.3	47.5	46.0	45.2	43.7	44.4	43.7	42.9	42.1	43.7	42.1
85°	28.3	28.3	27.6	26.0	27.6	26.8	26.0	26.0	25.3	25.3	25.3
87.5°	14.6	13.0	13.0	12.3	13.0	11.5	12.3	11.5	10.7	11.5	10.7
90°	29.0	30.1	31.1	32.2	32.7	33.0	33.5	34.0	34.5	35.0	34.5
92.5°	32.1	33.9	35.8	37.6	38.5	38.6	38.9	39.1	39.4	39.6	39.4
95°	37.9	39.7	41.6	43.4	44.3	44.3	44.3	44.3	44.3	44.3	44.3
97.5°	39.4	41.4	43.5	45.6	46.6	46.7	47.0	47.3	47.5	47.8	47.5
100°	40.6	42.6	44.7	46.8	47.8	47.9	48.2	48.5	48.7	49.0	48.7
102.5°	77.7	69.2	60.6	52.1	47.8	48.1	48.6	49.1	49.6	50.1	49.6
105°	209.5	163.7	117.8	71.9	49.0	49.3	49.8	50.3	50.8	51.3	50.8
107.5°	413.7	373.8	333.9	294.0	274.0	257.0	223.1	189.2	155.2	121.3	155.2
110°	517.3	508.8	500.2	491.7	487.4	468.9	431.8	394.8	357.7	320.7	357.7

TEST NUMBER: P1010636

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	601.7	604.1	606.4	608.7	609.9	609.6	609.1	608.6	608.0	607.5	608.0
115°	671.9	674.5	677.1	679.7	681.0	681.5	682.6	683.6	684.7	685.7	684.7
117.5°	740.2	742.3	744.4	746.5	747.5	747.6	747.9	748.1	748.4	748.6	748.4
120°	806.7	808.7	810.8	812.9	813.9	813.9	813.9	813.9	813.9	813.9	813.9
122.5°	872.4	873.7	875.0	876.3	876.9	877.0	877.3	877.6	877.8	878.1	877.8
125°	933.4	933.9	934.4	934.9	935.2	935.5	936.0	936.5	937.0	937.5	937.0
127.5°	995.5	996.3	997.0	997.8	998.2	997.9	997.4	996.9	996.3	995.8	996.3
130°	1050.5	1051.5	1052.6	1053.6	1054.1	1053.8	1053.3	1052.8	1052.3	1051.8	1052.3
132.5°	1102.9	1104.0	1105.0	1106.1	1106.6	1106.2	1105.4	1104.7	1103.9	1103.1	1103.9
135°	1156.4	1157.2	1157.9	1158.7	1159.1	1158.7	1157.9	1157.2	1156.4	1155.6	1156.4
137.5°	1203.5	1204.8	1206.1	1207.4	1208.1	1207.8	1207.3	1206.8	1206.2	1205.7	1206.2
140°	1248.7	1249.8	1250.8	1251.9	1252.4	1252.1	1251.6	1251.1	1250.5	1250.0	1250.5
142.5°	1291.6	1292.4	1293.1	1293.9	1294.3	1293.9	1293.1	1292.4	1291.6	1290.8	1291.6
145°	1331.0	1331.5	1332.0	1332.5	1332.8	1332.8	1332.8	1332.8	1332.8	1332.8	1332.8
147.5°	1367.1	1367.7	1368.2	1368.7	1369.0	1368.3	1367.0	1365.7	1364.4	1363.1	1364.4
150°	1399.8	1400.3	1400.8	1401.3	1401.6	1401.2	1400.4	1399.7	1398.9	1398.1	1398.9
152.5°	1428.3	1429.3	1430.4	1431.4	1431.9	1431.3	1430.0	1428.7	1427.4	1426.1	1427.4
155°	1454.2	1455.5	1456.8	1458.1	1458.8	1458.0	1456.5	1454.9	1453.4	1451.8	1453.4
157.5°	1477.8	1479.4	1480.9	1482.4	1483.2	1482.2	1480.1	1478.0	1476.0	1473.9	1476.0
160°	1497.7	1499.2	1500.8	1502.3	1503.1	1502.2	1500.4	1498.5	1496.7	1494.9	1496.7
162.5°	1515.4	1517.2	1519.0	1520.8	1521.7	1520.9	1519.4	1517.8	1516.3	1514.7	1516.3
165°	1530.8	1532.9	1535.0	1537.1	1538.1	1537.2	1535.4	1533.5	1531.7	1529.9	1531.7
167.5°	1543.7	1545.7	1547.8	1549.9	1550.9	1549.9	1547.8	1545.7	1543.7	1541.6	1543.7
170°	1554.1	1556.2	1558.3	1560.4	1561.4	1560.4	1558.3	1556.2	1554.1	1552.0	1554.1
172.5°	1561.1	1563.2	1565.3	1567.4	1568.4	1567.2	1564.9	1562.6	1560.2	1557.9	1560.2
175°	1566.7	1568.5	1570.3	1572.1	1573.0	1572.0	1569.9	1567.8	1565.8	1563.7	1565.8
177.5°	1569.3	1571.3	1573.4	1575.5	1576.5	1575.2	1572.6	1570.1	1567.5	1564.9	1567.5
180°	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5

TEST NUMBER: P1010636

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	847.2	849.5	843.4	841.9	841.9	844.9	842.6	822.0	825.8	821.2	819.7
5°	940.7	936.1	930.0	926.9	923.1	912.3	911.6	887.8	883.2	867.9	861.0
7.5°	1043.3	1039.5	1021.1	1018.8	1017.3	1007.3	982.1	956.8	938.4	920.8	903.9
10°	1160.5	1149.1	1140.6	1123.8	1115.3	1101.6	1068.6	1044.9	1013.5	986.7	951.4
12.5°	1301.5	1288.5	1260.1	1247.9	1237.1	1198.8	1165.9	1139.1	1077.8	1059.4	1015.8
15°	1404.9	1377.3	1374.3	1347.5	1345.9	1303.8	1241.0	1211.9	1164.4	1097.0	1051.8
17.5°	1516.7	1492.2	1473.1	1440.9	1436.3	1396.5	1350.5	1279.3	1227.2	1162.8	1105.4
20°	1598.7	1585.7	1552.8	1539.7	1512.9	1479.2	1431.7	1343.6	1280.0	1215.7	1145.2
22.5°	1663.8	1650.8	1624.8	1607.1	1591.8	1548.2	1491.5	1416.4	1329.1	1244.8	1172.0
25°	1663.1	1659.2	1648.5	1640.1	1628.6	1596.4	1548.9	1476.9	1379.6	1286.9	1185.8
27.5°	1568.8	1579.6	1597.9	1607.1	1604.8	1600.2	1573.4	1512.9	1425.6	1315.3	1201.9
30°	1372.7	1411.8	1446.3	1492.2	1506.0	1539.7	1555.1	1520.6	1450.9	1348.2	1222.6
32.5°	1138.3	1195.0	1270.1	1295.4	1339.0	1404.1	1476.9	1489.9	1446.3	1367.4	1235.6
35°	933.8	980.5	1038.7	1078.6	1117.6	1223.4	1315.3	1394.9	1409.5	1357.4	1232.5
37.5°	772.9	805.9	857.2	890.9	926.9	1017.3	1146.0	1249.4	1322.2	1323.7	1224.1
40°	656.5	671.0	715.5	740.0	774.5	852.6	967.5	1102.3	1208.8	1257.8	1201.9
42.5°	556.1	575.3	612.1	630.4	652.7	720.8	796.7	924.6	1056.4	1161.3	1160.5
45°	496.4	510.2	527.0	542.4	567.6	608.2	694.8	790.5	916.9	1035.7	1082.4
47.5°	443.5	456.6	473.4	478.0	494.9	533.2	586.0	669.5	787.5	905.5	993.5
50°	399.1	409.8	421.3	429.7	437.4	468.8	508.6	579.1	673.3	787.5	897.0
52.5°	364.6	372.3	382.3	386.8	393.7	416.7	447.4	499.5	576.8	681.0	787.5
55°	332.5	337.8	343.9	351.6	354.7	371.5	395.3	439.7	497.2	590.6	691.7
57.5°	302.6	304.9	308.7	313.3	317.1	331.7	352.4	382.3	432.8	504.8	600.6
60°	268.9	275.0	277.3	281.9	284.2	295.7	311.8	337.1	376.1	438.2	510.2
62.5°	240.5	244.4	248.2	250.5	255.9	259.7	272.7	295.7	327.9	373.8	438.9
65°	215.3	216.8	219.1	221.4	222.9	227.5	239.8	255.1	279.6	320.2	370.8
67.5°	186.1	187.7	190.7	191.5	193.0	199.2	206.1	219.1	239.8	270.4	311.8
70°	157.8	160.1	161.6	163.2	165.5	167.8	175.4	186.1	202.2	223.7	255.9
72.5°	133.3	135.6	135.6	137.1	136.4	139.4	147.1	154.7	165.5	183.1	211.4
75°	108.8	108.8	110.3	111.1	111.8	114.9	118.0	124.1	132.5	146.3	163.9
77.5°	85.8	85.0	86.6	86.6	86.6	88.9	91.9	95.0	100.4	110.3	124.1
80°	62.8	62.8	64.3	65.1	63.6	64.3	65.9	68.9	72.8	79.7	87.3
82.5°	41.4	44.4	43.7	44.4	43.7	45.2	46.0	46.7	48.3	51.3	56.7
85°	25.3	25.3	25.3	26.0	25.3	26.0	26.0	26.0	26.8	28.3	30.6
87.5°	10.7	10.7	10.7	11.5	10.7	10.7	11.5	10.7	11.5	11.5	12.3
90°	34.0	33.5	33.0	32.7	32.2	31.1	30.1	29.0	28.0	24.6	21.2
92.5°	39.1	38.9	38.6	38.5	37.6	35.8	33.9	32.1	30.3	28.0	25.6
95°	44.3	44.3	44.3	44.3	43.4	41.6	39.7	37.9	36.1	33.3	30.4
97.5°	47.3	47.0	46.7	46.6	45.6	43.5	41.4	39.4	37.3	50.5	63.7
100°	48.5	48.2	47.9	47.8	46.8	44.7	42.6	40.6	38.5	78.9	119.3
102.5°	49.1	48.6	48.1	47.8	52.1	60.6	69.2	77.7	86.3	131.4	176.5
105°	50.3	49.8	49.3	49.0	71.9	117.8	163.7	209.5	255.4	278.7	302.0
107.5°	189.2	223.1	257.0	274.0	294.0	333.9	373.8	413.7	453.6	449.7	445.8
110°	394.8	431.8	468.9	487.4	491.7	500.2	508.8	517.3	525.9	523.1	520.2

TEST NUMBER: P1010636

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	608.6	609.1	609.6	609.9	608.7	606.4	604.1	601.7	599.4	596.5	593.7
115°	683.6	682.6	681.5	681.0	679.7	677.1	674.5	671.9	669.3	667.0	664.6
117.5°	748.1	747.9	747.6	747.5	746.5	744.4	742.3	740.2	738.1	736.8	735.5
120°	813.9	813.9	813.9	813.9	812.9	810.8	808.7	806.7	804.6	803.8	803.0
122.5°	877.6	877.3	877.0	876.9	876.3	875.0	873.7	872.4	871.1	870.1	869.0
125°	936.5	936.0	935.5	935.2	934.9	934.4	933.9	933.4	932.9	931.9	930.8
127.5°	996.9	997.4	997.9	998.2	997.8	997.0	996.3	995.5	994.7	993.4	992.1
130°	1052.8	1053.3	1053.8	1054.1	1053.6	1052.6	1051.5	1050.5	1049.5	1048.5	1047.4
132.5°	1104.7	1105.4	1106.2	1106.6	1106.1	1105.0	1104.0	1102.9	1101.9	1101.1	1100.3
135°	1157.2	1157.9	1158.7	1159.1	1158.7	1157.9	1157.2	1156.4	1155.6	1154.6	1153.5
137.5°	1206.8	1207.3	1207.8	1208.1	1207.4	1206.1	1204.8	1203.5	1202.2	1201.7	1201.2
140°	1251.1	1251.6	1252.1	1252.4	1251.9	1250.8	1249.8	1248.7	1247.7	1246.9	1246.1
142.5°	1292.4	1293.1	1293.9	1294.3	1293.9	1293.1	1292.4	1291.6	1290.8	1290.0	1289.2
145°	1332.8	1332.8	1332.8	1332.8	1332.5	1332.0	1331.5	1331.0	1330.5	1330.0	1329.5
147.5°	1365.7	1367.0	1368.3	1369.0	1368.7	1368.2	1367.7	1367.1	1366.6	1366.1	1365.6
150°	1399.7	1400.4	1401.2	1401.6	1401.3	1400.8	1400.3	1399.8	1399.3	1398.8	1398.3
152.5°	1428.7	1430.0	1431.3	1431.9	1431.4	1430.4	1429.3	1428.3	1427.3	1427.0	1426.8
155°	1454.9	1456.5	1458.0	1458.8	1458.1	1456.8	1455.5	1454.2	1452.9	1452.7	1452.4
157.5°	1478.0	1480.1	1482.2	1483.2	1482.4	1480.9	1479.4	1477.8	1476.3	1476.5	1476.8
160°	1498.5	1500.4	1502.2	1503.1	1502.3	1500.8	1499.2	1497.7	1496.1	1496.3	1496.6
162.5°	1517.8	1519.4	1520.9	1521.7	1520.8	1519.0	1517.2	1515.4	1513.6	1513.8	1514.1
165°	1533.5	1535.4	1537.2	1538.1	1537.1	1535.0	1532.9	1530.8	1528.7	1529.0	1529.2
167.5°	1545.7	1547.8	1549.9	1550.9	1549.9	1547.8	1545.7	1543.7	1541.6	1541.6	1541.6
170°	1556.2	1558.3	1560.4	1561.4	1560.4	1558.3	1556.2	1554.1	1552.0	1552.0	1552.0
172.5°	1562.6	1564.9	1567.2	1568.4	1567.4	1565.3	1563.2	1561.1	1559.0	1558.8	1558.5
175°	1567.8	1569.9	1572.0	1573.0	1572.1	1570.3	1568.5	1566.7	1564.9	1564.6	1564.4
177.5°	1570.1	1572.6	1575.2	1576.5	1575.5	1573.4	1571.3	1569.3	1567.2	1566.9	1566.7
180°	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5

TEST NUMBER: P1010636

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	812.0	809.7	809.7	808.2	803.6	795.1	794.4	795.9	791.3	786.7	779.8
5°	851.8	837.3	832.7	828.1	818.9	803.6	797.4	792.1	783.7	773.7	763.0
7.5°	885.5	864.9	858.7	850.3	831.9	810.5	796.7	785.2	773.7	759.9	746.9
10°	927.7	897.8	883.2	871.0	845.7	815.8	795.1	778.3	759.9	743.1	726.2
12.5°	975.2	926.9	922.3	892.4	863.3	818.9	793.6	769.1	744.6	723.9	706.3
15°	1015.0	962.1	943.0	923.1	867.2	812.0	787.5	759.9	731.6	709.3	683.3
17.5°	1040.3	996.6	956.0	929.2	871.0	822.0	774.5	743.1	713.2	682.5	661.1
20°	1070.9	1007.3	972.1	936.1	878.6	814.3	766.8	727.7	691.0	663.4	637.3
22.5°	1101.6	1015.8	986.7	947.6	880.2	806.6	753.0	713.9	671.8	644.2	615.9
25°	1098.5	1028.0	979.8	946.8	864.9	799.7	736.9	691.0	651.9	616.7	588.3
27.5°	1100.8	1014.2	965.2	926.9	854.1	789.8	720.1	671.8	631.2	594.4	564.6
30°	1101.6	993.5	950.6	904.7	834.2	766.0	700.9	651.9	609.0	569.2	542.4
32.5°	1099.3	976.7	923.1	881.7	802.8	743.1	678.7	626.6	583.0	546.2	520.9
35°	1093.9	956.8	894.7	842.6	770.6	710.1	658.0	604.4	557.7	524.0	494.9
37.5°	1079.3	935.3	864.9	813.5	733.1	671.8	625.9	581.4	536.2	496.4	471.9
40°	1068.6	906.2	835.0	779.1	692.5	632.7	594.4	552.3	507.9	471.9	448.1
42.5°	1044.1	878.6	804.3	737.7	652.7	591.4	555.4	521.7	483.4	448.1	426.7
45°	1004.3	848.8	766.8	699.4	609.0	550.8	517.8	490.3	456.6	422.9	401.4
47.5°	948.4	805.9	727.0	659.6	566.1	507.1	474.2	453.5	426.7	398.3	380.0
50°	887.8	759.1	686.4	619.7	524.7	467.3	435.1	416.0	398.3	372.3	354.7
52.5°	808.9	709.3	639.6	576.1	480.3	425.1	396.8	383.0	364.6	346.2	330.9
55°	732.3	645.0	587.5	527.0	436.6	385.3	357.7	343.2	332.5	317.1	304.9
57.5°	643.5	585.3	532.4	477.2	396.0	349.3	323.3	305.6	298.8	291.9	280.4
60°	561.5	517.1	474.2	428.2	353.9	311.8	286.5	272.7	265.8	261.2	253.6
62.5°	486.4	452.0	415.2	378.4	311.0	272.7	253.6	239.8	233.6	232.9	226.0
65°	414.4	389.9	360.0	324.0	271.2	237.5	219.1	210.7	203.8	203.8	198.4
67.5°	342.4	325.6	301.8	276.5	235.2	203.8	186.9	179.3	175.4	175.4	171.6
70°	285.0	273.5	252.0	229.8	193.8	170.1	157.0	150.1	147.8	148.6	145.5
72.5°	231.3	219.1	201.5	185.4	158.6	141.0	131.8	124.1	120.3	121.0	120.3
75°	179.3	173.1	157.8	145.5	124.1	111.8	103.4	99.6	96.5	97.3	95.8
77.5°	134.8	125.6	117.2	108.8	95.8	85.8	78.9	75.1	72.8	72.8	72.8
80°	91.9	90.4	83.5	78.9	68.2	60.5	55.2	54.4	52.1	52.1	52.1
82.5°	59.8	55.9	52.1	49.0	42.9	38.3	36.0	34.5	33.7	32.9	34.5
85°	32.9	30.6	29.1	26.0	23.7	21.4	19.2	18.4	17.6	18.4	17.6
87.5°	13.0	10.7	10.7	10.0	9.2	8.4	8.4	6.9	6.9	6.1	6.1
90°	17.9	14.5	12.8	11.5	8.9	6.4	3.8	1.2	3.8	6.4	8.9
92.5°	23.3	21.0	19.8	20.6	22.1	23.7	25.2	26.8	25.2	23.7	22.1
95°	27.6	24.7	23.3	28.6	39.2	49.9	60.5	71.1	60.5	49.9	39.2
97.5°	77.0	90.2	96.8	100.4	107.7	114.9	122.2	129.4	122.2	114.9	107.7
100°	159.8	200.2	220.4	217.8	212.6	207.5	202.3	197.1	202.3	207.5	212.6
102.5°	221.6	266.7	289.2	287.5	284.1	280.8	277.4	274.0	277.4	280.8	284.1
105°	325.3	348.6	360.3	358.9	356.0	353.2	350.3	347.5	350.3	353.2	356.0
107.5°	441.9	438.0	436.1	434.9	432.6	430.3	427.9	425.6	427.9	430.3	432.6
110°	517.4	514.5	513.1	512.1	510.0	507.9	505.8	503.7	505.8	507.9	510.0

TEST NUMBER: P1010636

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	590.8	587.9	586.5	585.6	583.8	582.0	580.2	578.4	580.2	582.0	583.8
115°	662.3	660.0	658.8	658.0	656.5	654.9	653.4	651.8	653.4	654.9	656.5
117.5°	734.2	732.9	732.3	731.4	729.6	727.7	725.9	724.1	725.9	727.7	729.6
120°	802.3	801.5	801.1	799.9	797.6	795.3	792.9	790.6	792.9	795.3	797.6
122.5°	868.0	866.9	866.4	865.5	863.7	861.8	860.0	858.2	860.0	861.8	863.7
125°	929.8	928.7	928.2	927.2	925.1	923.0	921.0	918.9	921.0	923.0	925.1
127.5°	990.8	989.5	988.8	987.8	985.7	983.6	981.6	979.5	981.6	983.6	985.7
130°	1046.4	1045.3	1044.8	1043.8	1041.7	1039.6	1037.6	1035.5	1037.6	1039.6	1041.7
132.5°	1099.6	1098.8	1098.4	1097.4	1095.3	1093.2	1091.2	1089.1	1091.2	1093.2	1095.3
135°	1152.5	1151.4	1150.9	1150.1	1148.6	1147.0	1145.5	1143.9	1145.5	1147.0	1148.6
137.5°	1200.7	1200.2	1199.9	1198.9	1196.8	1194.7	1192.7	1190.6	1192.7	1194.7	1196.8
140°	1245.4	1244.6	1244.2	1243.4	1241.9	1240.3	1238.8	1237.2	1238.8	1240.3	1241.9
142.5°	1288.5	1287.7	1287.3	1286.5	1285.0	1283.5	1281.9	1280.4	1281.9	1283.5	1285.0
145°	1329.0	1328.5	1328.2	1327.3	1325.5	1323.6	1321.8	1320.0	1321.8	1323.6	1325.5
147.5°	1365.1	1364.6	1364.3	1363.7	1362.4	1361.1	1359.8	1358.5	1359.8	1361.1	1362.4
150°	1397.8	1397.3	1397.0	1396.6	1395.8	1395.1	1394.3	1393.5	1394.3	1395.1	1395.8
152.5°	1426.5	1426.2	1426.1	1426.0	1425.7	1425.4	1425.2	1424.9	1425.2	1425.4	1425.7
155°	1452.2	1451.9	1451.8	1452.1	1452.6	1453.1	1453.6	1454.1	1453.6	1453.1	1452.6
157.5°	1477.0	1477.3	1477.4	1477.4	1477.4	1477.4	1477.4	1477.4	1477.4	1477.4	1477.4
160°	1496.8	1497.1	1497.2	1497.3	1497.6	1497.9	1498.1	1498.4	1498.1	1497.9	1497.6
162.5°	1514.3	1514.6	1514.7	1515.1	1515.9	1516.6	1517.4	1518.2	1517.4	1516.6	1515.9
165°	1529.5	1529.8	1529.9	1530.3	1531.1	1531.8	1532.6	1533.4	1532.6	1531.8	1531.1
167.5°	1541.6	1541.6	1541.6	1542.1	1543.1	1544.2	1545.2	1546.2	1545.2	1544.2	1543.1
170°	1552.0	1552.0	1552.0	1552.5	1553.6	1554.6	1555.7	1556.7	1555.7	1554.6	1553.6
172.5°	1558.3	1558.0	1557.9	1558.5	1559.8	1561.1	1562.4	1563.7	1562.4	1561.1	1559.8
175°	1564.1	1563.8	1563.7	1564.3	1565.6	1566.9	1568.2	1569.5	1568.2	1566.9	1565.6
177.5°	1566.4	1566.1	1566.0	1566.7	1568.0	1569.3	1570.6	1571.9	1570.6	1569.3	1568.0
180°	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5

TEST NUMBER: P1010636

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	778.3	777.5	779.1	774.5	766.8	763.0	752.2	749.9	749.2	749.9	750.7
5°	756.8	756.1	753.8	746.1	736.9	730.0	717.0	716.2	711.6	707.0	709.3
7.5°	736.2	733.1	728.5	718.5	706.3	698.6	687.9	680.2	674.1	670.3	667.2
10°	715.5	710.9	706.3	693.3	677.9	666.5	653.4	647.3	640.4	637.3	634.3
12.5°	688.7	684.1	675.6	660.3	651.1	636.6	623.6	617.4	613.6	607.5	603.6
15°	667.2	658.0	653.4	637.3	618.2	616.7	592.9	591.4	583.7	583.7	577.6
17.5°	642.7	635.8	627.4	611.3	597.5	583.7	571.5	566.9	560.0	558.4	555.4
20°	619.0	609.8	606.7	590.6	576.1	559.2	546.2	541.6	538.5	535.5	537.8
22.5°	594.4	586.8	579.1	564.6	553.8	537.0	529.3	524.7	520.1	518.6	519.4
25°	570.7	563.8	556.1	541.6	530.1	516.3	509.4	507.1	504.8	504.8	504.1
27.5°	547.7	540.8	533.9	520.9	509.4	499.5	494.1	491.8	489.5	491.0	492.6
30°	524.0	517.8	511.7	500.2	491.0	481.8	478.8	477.2	476.5	480.3	480.3
32.5°	502.5	497.2	492.6	481.8	472.6	465.0	462.7	463.5	464.2	466.5	468.0
35°	480.3	476.5	471.9	462.7	455.0	448.1	448.9	448.9	450.4	454.3	457.3
37.5°	460.4	455.0	451.2	443.5	437.4	431.3	433.6	435.9	437.4	442.0	443.5
40°	436.6	434.3	431.3	423.6	418.3	417.5	418.3	419.8	422.9	425.1	427.4
42.5°	417.5	414.4	410.6	404.5	399.9	400.6	401.4	402.9	404.5	408.3	410.6
45°	396.0	393.7	390.7	385.3	381.5	382.3	383.0	383.0	384.5	389.1	390.7
47.5°	372.3	373.1	369.2	363.9	361.6	361.6	361.6	363.1	366.9	368.5	369.2
50°	349.3	347.8	347.0	341.7	340.1	339.4	340.1	340.9	346.2	345.5	347.8
52.5°	324.8	324.8	324.0	321.0	318.7	318.7	317.1	321.0	322.5	324.0	326.3
55°	301.1	298.8	298.0	296.5	293.4	292.6	294.2	298.8	300.3	301.8	304.1
57.5°	275.0	275.0	273.5	271.2	271.2	271.2	271.2	274.2	276.5	278.1	282.7
60°	251.3	248.2	245.9	245.9	245.9	245.1	249.7	249.7	254.3	255.1	256.6
62.5°	222.9	221.4	219.9	220.6	219.9	221.4	222.9	226.0	226.7	229.0	231.3
65°	196.1	196.1	194.6	199.2	196.1	196.1	199.9	199.9	201.5	203.8	206.8
67.5°	170.1	170.8	169.3	169.3	170.8	171.6	172.4	175.4	176.2	179.3	183.1
70°	143.2	144.8	145.5	144.0	145.5	147.1	148.6	149.4	152.4	154.0	156.3
72.5°	119.5	121.0	118.7	119.5	120.3	121.8	122.6	124.1	125.6	130.2	131.8
75°	95.8	95.0	94.2	97.3	95.8	98.8	99.6	99.6	101.1	104.9	106.5
77.5°	73.5	73.5	74.3	72.8	75.1	74.3	75.1	77.4	79.7	79.7	85.8
80°	51.3	52.9	52.9	52.9	53.6	54.4	52.9	56.7	57.5	57.5	59.8
82.5°	32.9	33.7	32.9	34.5	34.5	36.0	35.2	36.0	37.5	39.1	39.8
85°	17.6	17.6	19.2	19.2	18.4	19.2	18.4	19.2	20.7	20.7	21.4
87.5°	6.1	6.1	6.1	6.1	6.9	6.1	6.9	6.9	6.1	6.1	8.4
90°	11.5	12.8	14.5	17.9	21.2	24.6	28.0	29.0	30.1	31.1	32.2
92.5°	20.6	19.8	21.0	23.3	25.6	28.0	30.3	32.1	33.9	35.8	37.6
95°	28.6	23.3	24.7	27.6	30.4	33.3	36.1	37.9	39.7	41.6	43.4
97.5°	100.4	96.8	90.2	77.0	63.7	50.5	37.3	39.4	41.4	43.5	45.6
100°	217.8	220.4	200.2	159.8	119.3	78.9	38.5	40.6	42.6	44.7	46.8
102.5°	287.5	289.2	266.7	221.6	176.5	131.4	86.3	77.7	69.2	60.6	52.1
105°	358.9	360.3	348.6	325.3	302.0	278.7	255.4	209.5	163.7	117.8	71.9
107.5°	434.9	436.1	438.0	441.9	445.8	449.7	453.6	413.7	373.8	333.9	294.0
110°	512.1	513.1	514.5	517.4	520.2	523.1	525.9	517.3	508.8	500.2	491.7

TEST NUMBER: P1010636

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	585.6	586.5	587.9	590.8	593.7	596.5	599.4	601.7	604.1	606.4	608.7
115°	658.0	658.8	660.0	662.3	664.6	667.0	669.3	671.9	674.5	677.1	679.7
117.5°	731.4	732.3	732.9	734.2	735.5	736.8	738.1	740.2	742.3	744.4	746.5
120°	799.9	801.1	801.5	802.3	803.0	803.8	804.6	806.7	808.7	810.8	812.9
122.5°	865.5	866.4	866.9	868.0	869.0	870.1	871.1	872.4	873.7	875.0	876.3
125°	927.2	928.2	928.7	929.8	930.8	931.9	932.9	933.4	933.9	934.4	934.9
127.5°	987.8	988.8	989.5	990.8	992.1	993.4	994.7	995.5	996.3	997.0	997.8
130°	1043.8	1044.8	1045.3	1046.4	1047.4	1048.5	1049.5	1050.5	1051.5	1052.6	1053.6
132.5°	1097.4	1098.4	1098.8	1099.6	1100.3	1101.1	1101.9	1102.9	1104.0	1105.0	1106.1
135°	1150.1	1150.9	1151.4	1152.5	1153.5	1154.6	1155.6	1156.4	1157.2	1157.9	1158.7
137.5°	1198.9	1199.9	1200.2	1200.7	1201.2	1201.7	1202.2	1203.5	1204.8	1206.1	1207.4
140°	1243.4	1244.2	1244.6	1245.4	1246.1	1246.9	1247.7	1248.7	1249.8	1250.8	1251.9
142.5°	1286.5	1287.3	1287.7	1288.5	1289.2	1290.0	1290.8	1291.6	1292.4	1293.1	1293.9
145°	1327.3	1328.2	1328.5	1329.0	1329.5	1330.0	1330.5	1331.0	1331.5	1332.0	1332.5
147.5°	1363.7	1364.3	1364.6	1365.1	1365.6	1366.1	1366.6	1367.1	1367.7	1368.2	1368.7
150°	1396.6	1397.0	1397.3	1397.8	1398.3	1398.8	1399.3	1399.8	1400.3	1400.8	1401.3
152.5°	1426.0	1426.1	1426.2	1426.5	1426.8	1427.0	1427.3	1428.3	1429.3	1430.4	1431.4
155°	1452.1	1451.8	1451.9	1452.2	1452.4	1452.7	1452.9	1454.2	1455.5	1456.8	1458.1
157.5°	1477.4	1477.4	1477.3	1477.0	1476.8	1476.5	1476.3	1477.8	1479.4	1480.9	1482.4
160°	1497.3	1497.2	1497.1	1496.8	1496.6	1496.3	1496.1	1497.7	1499.2	1500.8	1502.3
162.5°	1515.1	1514.7	1514.6	1514.3	1514.1	1513.8	1513.6	1515.4	1517.2	1519.0	1520.8
165°	1530.3	1529.9	1529.8	1529.5	1529.2	1529.0	1528.7	1530.8	1532.9	1535.0	1537.1
167.5°	1542.1	1541.6	1541.6	1541.6	1541.6	1541.6	1541.6	1543.7	1545.7	1547.8	1549.9
170°	1552.5	1552.0	1552.0	1552.0	1552.0	1552.0	1552.0	1554.1	1556.2	1558.3	1560.4
172.5°	1558.5	1557.9	1558.0	1558.3	1558.5	1558.8	1559.0	1561.1	1563.2	1565.3	1567.4
175°	1564.3	1563.7	1563.8	1564.1	1564.4	1564.6	1564.9	1566.7	1568.5	1570.3	1572.1
177.5°	1566.7	1566.0	1566.1	1566.4	1566.7	1566.9	1567.2	1569.3	1571.3	1573.4	1575.5
180°	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5

TEST NUMBER: P1010636

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	749.9	750.7	747.6	745.4	751.5	747.6	747.6	748.4	746.9	749.2	748.4
5°	707.8	708.6	703.2	704.8	701.7	700.9	700.2	704.8	704.0	703.2	704.8
7.5°	666.5	666.5	664.2	662.6	662.6	660.3	663.4	662.6	664.2	664.2	666.5
10°	632.0	633.5	629.7	625.9	625.1	625.9	625.9	626.6	627.4	632.7	632.0
12.5°	603.6	601.3	600.6	598.3	594.4	592.9	591.4	599.8	597.5	597.5	597.5
15°	572.2	577.6	576.8	569.9	568.4	571.5	569.9	569.9	577.6	576.8	576.1
17.5°	555.4	553.8	552.3	548.5	549.2	548.5	549.2	549.2	553.8	553.8	553.8
20°	536.2	533.2	533.2	531.6	531.6	529.3	532.4	533.2	536.2	536.2	537.0
22.5°	519.4	517.1	517.1	516.3	517.8	514.8	517.8	518.6	518.6	520.9	520.9
25°	504.8	503.3	503.3	504.8	504.8	504.8	504.8	507.9	505.6	506.3	505.6
27.5°	491.8	492.6	493.3	494.1	493.3	494.1	494.9	496.4	497.2	496.4	494.9
30°	479.5	481.8	482.6	482.6	484.1	484.9	485.7	485.7	486.4	484.1	485.7
32.5°	470.3	470.3	471.9	472.6	474.2	474.9	474.9	476.5	475.7	473.4	474.2
35°	457.3	457.3	460.4	461.9	464.2	463.5	464.2	464.2	465.0	463.5	461.2
37.5°	444.3	445.8	445.8	448.9	449.7	450.4	449.7	451.2	450.4	448.9	448.1
40°	429.0	428.2	429.0	431.3	432.0	432.0	432.0	433.6	433.6	433.6	432.8
42.5°	409.8	412.1	411.4	413.7	412.9	412.9	414.4	416.0	416.7	414.4	415.2
45°	391.4	391.4	393.0	393.0	393.7	393.7	396.8	395.3	396.8	395.3	396.0
47.5°	371.5	372.3	372.3	373.1	374.6	376.1	374.6	375.4	375.4	376.1	374.6
50°	349.3	349.3	350.8	353.1	356.2	354.7	353.9	357.0	354.7	354.7	353.1
52.5°	326.3	328.6	329.4	331.7	334.0	334.8	335.5	334.0	334.8	332.5	333.2
55°	304.1	304.9	307.9	310.2	312.5	312.5	311.8	312.5	313.3	310.2	310.2
57.5°	281.9	284.2	287.3	287.3	290.3	290.3	289.6	289.6	290.3	288.0	287.3
60°	258.2	260.5	264.3	264.3	268.9	269.6	268.1	266.6	266.6	264.3	265.0
62.5°	232.9	235.2	237.5	241.3	244.4	242.8	245.9	242.8	243.6	239.0	239.0
65°	210.7	211.4	215.3	219.1	219.1	220.6	219.1	219.9	217.6	217.6	214.5
67.5°	184.6	184.6	188.4	192.3	196.1	196.1	196.1	193.8	193.8	191.5	191.5
70°	161.6	160.9	164.7	167.0	169.3	170.1	168.5	167.8	166.2	163.9	163.2
72.5°	133.3	134.8	138.7	140.2	144.0	143.2	147.1	142.5	142.5	138.7	137.9
75°	108.0	109.5	113.4	115.7	118.0	118.0	120.3	118.0	114.9	113.4	112.6
77.5°	85.8	85.0	88.1	91.9	92.7	91.9	93.5	92.7	89.6	89.6	88.1
80°	61.3	63.6	66.6	65.9	68.9	68.2	68.2	66.6	66.6	64.3	65.9
82.5°	40.6	42.9	43.7	42.9	43.7	45.2	46.0	45.2	45.2	43.7	44.4
85°	21.4	21.4	23.0	23.7	23.0	23.0	23.7	26.0	24.5	23.0	24.5
87.5°	6.9	6.1	6.1	6.9	6.1	6.1	6.9	6.9	7.7	7.7	7.7
90°	32.7	33.0	33.5	34.0	34.5	35.0	34.5	34.0	33.5	33.0	32.7
92.5°	38.5	38.6	38.9	39.1	39.4	39.6	39.4	39.1	38.9	38.6	38.5
95°	44.3	44.3	44.3	44.3	44.3	44.3	44.3	44.3	44.3	44.3	44.3
97.5°	46.6	46.7	47.0	47.3	47.5	47.8	47.5	47.3	47.0	46.7	46.6
100°	47.8	47.9	48.2	48.5	48.7	49.0	48.7	48.5	48.2	47.9	47.8
102.5°	47.8	48.1	48.6	49.1	49.6	50.1	49.6	49.1	48.6	48.1	47.8
105°	49.0	49.3	49.8	50.3	50.8	51.3	50.8	50.3	49.8	49.3	49.0
107.5°	274.0	257.0	223.1	189.2	155.2	121.3	155.2	189.2	223.1	257.0	274.0
110°	487.4	468.9	431.8	394.8	357.7	320.7	357.7	394.8	431.8	468.9	487.4

TEST NUMBER: P1010636

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	609.9	609.6	609.1	608.6	608.0	607.5	608.0	608.6	609.1	609.6	609.9
115°	681.0	681.5	682.6	683.6	684.7	685.7	684.7	683.6	682.6	681.5	681.0
117.5°	747.5	747.6	747.9	748.1	748.4	748.6	748.4	748.1	747.9	747.6	747.5
120°	813.9	813.9	813.9	813.9	813.9	813.9	813.9	813.9	813.9	813.9	813.9
122.5°	876.9	877.0	877.3	877.6	877.8	878.1	877.8	877.6	877.3	877.0	876.9
125°	935.2	935.5	936.0	936.5	937.0	937.5	937.0	936.5	936.0	935.5	935.2
127.5°	998.2	997.9	997.4	996.9	996.3	995.8	996.3	996.9	997.4	997.9	998.2
130°	1054.1	1053.8	1053.3	1052.8	1052.3	1051.8	1052.3	1052.8	1053.3	1053.8	1054.1
132.5°	1106.6	1106.2	1105.4	1104.7	1103.9	1103.1	1103.9	1104.7	1105.4	1106.2	1106.6
135°	1159.1	1158.7	1157.9	1157.2	1156.4	1155.6	1156.4	1157.2	1157.9	1158.7	1159.1
137.5°	1208.1	1207.8	1207.3	1206.8	1206.2	1205.7	1206.2	1206.8	1207.3	1207.8	1208.1
140°	1252.4	1252.1	1251.6	1251.1	1250.5	1250.0	1250.5	1251.1	1251.6	1252.1	1252.4
142.5°	1294.3	1293.9	1293.1	1292.4	1291.6	1290.8	1291.6	1292.4	1293.1	1293.9	1294.3
145°	1332.8	1332.8	1332.8	1332.8	1332.8	1332.8	1332.8	1332.8	1332.8	1332.8	1332.8
147.5°	1369.0	1368.3	1367.0	1365.7	1364.4	1363.1	1364.4	1365.7	1367.0	1368.3	1369.0
150°	1401.6	1401.2	1400.4	1399.7	1398.9	1398.1	1398.9	1399.7	1400.4	1401.2	1401.6
152.5°	1431.9	1431.3	1430.0	1428.7	1427.4	1426.1	1427.4	1428.7	1430.0	1431.3	1431.9
155°	1458.8	1458.0	1456.5	1454.9	1453.4	1451.8	1453.4	1454.9	1456.5	1458.0	1458.8
157.5°	1483.2	1482.2	1480.1	1478.0	1476.0	1473.9	1476.0	1478.0	1480.1	1482.2	1483.2
160°	1503.1	1502.2	1500.4	1498.5	1496.7	1494.9	1496.7	1498.5	1500.4	1502.2	1503.1
162.5°	1521.7	1520.9	1519.4	1517.8	1516.3	1514.7	1516.3	1517.8	1519.4	1520.9	1521.7
165°	1538.1	1537.2	1535.4	1533.5	1531.7	1529.9	1531.7	1533.5	1535.4	1537.2	1538.1
167.5°	1550.9	1549.9	1547.8	1545.7	1543.7	1541.6	1543.7	1545.7	1547.8	1549.9	1550.9
170°	1561.4	1560.4	1558.3	1556.2	1554.1	1552.0	1554.1	1556.2	1558.3	1560.4	1561.4
172.5°	1568.4	1567.2	1564.9	1562.6	1560.2	1557.9	1560.2	1562.6	1564.9	1567.2	1568.4
175°	1573.0	1572.0	1569.9	1567.8	1565.8	1563.7	1565.8	1567.8	1569.9	1572.0	1573.0
177.5°	1576.5	1575.2	1572.6	1570.1	1567.5	1564.9	1567.5	1570.1	1572.6	1575.2	1576.5
180°	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5

TEST NUMBER: P1010636

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	750.7	752.2	753.0	749.9	747.6	751.5	756.8	760.7	763.7	767.6	769.9
5°	706.3	711.6	711.6	713.2	715.5	719.3	729.3	736.2	742.3	746.9	750.7
7.5°	668.7	672.6	674.9	678.7	682.5	687.9	699.4	709.3	718.5	723.9	730.0
10°	635.0	638.1	641.9	644.2	651.1	658.8	673.3	681.8	692.5	700.9	708.6
12.5°	602.9	613.6	615.9	615.1	621.3	629.7	644.2	657.3	668.7	677.2	685.6
15°	579.9	583.7	588.3	587.5	600.6	602.9	615.1	630.4	645.8	651.1	658.8
17.5°	554.6	560.7	565.3	567.6	571.5	579.9	591.4	602.9	622.8	623.6	643.5
20°	534.7	540.8	543.9	546.9	549.2	559.2	569.2	582.2	598.3	606.7	617.4
22.5°	521.7	524.7	527.0	529.3	532.4	537.8	550.0	564.6	575.3	584.5	591.4
25°	506.3	509.4	512.5	514.0	516.3	519.4	528.6	540.1	555.4	561.5	568.4
27.5°	495.6	495.6	497.2	497.2	500.2	503.3	510.2	520.9	533.2	540.8	550.0
30°	484.1	483.4	484.1	483.4	482.6	487.2	493.3	502.5	510.9	520.1	526.3
32.5°	472.6	471.9	471.9	472.6	469.6	471.9	474.9	483.4	492.6	497.2	504.1
35°	460.4	458.9	458.9	458.9	457.3	455.8	458.9	466.5	472.6	478.8	484.1
37.5°	448.1	445.8	445.8	444.3	442.8	440.5	440.5	446.6	455.0	457.3	464.2
40°	431.3	431.3	429.7	429.0	427.4	425.9	423.6	429.0	436.6	438.9	444.3
42.5°	414.4	412.1	411.4	411.4	411.4	409.1	407.5	411.4	416.0	419.8	422.9
45°	395.3	393.7	394.5	393.7	392.2	391.4	390.7	392.2	397.6	399.1	402.9
47.5°	374.6	373.8	373.8	373.1	372.3	373.1	370.0	373.8	375.4	376.9	380.0
50°	353.1	352.4	351.6	350.8	350.8	351.6	350.8	350.8	353.9	355.4	358.5
52.5°	331.7	329.4	329.4	328.6	328.6	327.1	328.6	329.4	330.9	332.5	334.0
55°	308.7	308.7	306.4	306.4	304.9	304.9	305.6	304.9	307.9	309.5	309.5
57.5°	286.5	283.4	284.2	282.7	281.1	280.4	280.4	281.9	283.4	283.4	285.0
60°	262.7	259.7	258.9	255.9	257.4	255.1	255.9	255.9	258.9	257.4	258.9
62.5°	239.0	235.2	232.9	231.3	231.3	232.1	230.6	229.8	231.3	232.9	235.9
65°	213.7	211.4	209.1	206.8	206.8	206.1	207.6	205.3	204.5	205.3	206.8
67.5°	187.7	185.4	183.1	180.8	181.6	179.3	177.7	180.0	178.5	179.3	180.8
70°	162.4	160.9	156.3	154.7	154.0	154.7	154.0	152.4	154.7	154.0	154.7
72.5°	137.1	135.6	133.3	129.5	129.5	128.7	127.9	127.9	127.2	127.2	127.2
75°	112.6	109.5	107.2	106.5	104.9	104.2	103.4	101.9	102.6	103.4	101.9
77.5°	87.3	83.5	82.7	82.7	80.4	80.4	81.2	80.4	79.7	79.7	79.7
80°	64.3	61.3	61.3	59.8	58.2	58.2	58.2	58.2	57.5	56.7	57.5
82.5°	41.4	40.6	39.8	39.8	41.4	38.3	39.8	39.1	38.3	38.3	37.5
85°	23.0	23.7	23.0	23.7	22.2	23.0	23.0	23.0	22.2	23.0	21.4
87.5°	8.4	8.4	8.4	9.2	9.2	9.2	9.2	9.2	10.0	9.2	9.2
90°	32.2	31.1	30.1	29.0	28.0	24.6	21.2	17.9	14.5	12.8	11.5
92.5°	37.6	35.8	33.9	32.1	30.3	28.0	25.6	23.3	21.0	19.8	20.6
95°	43.4	41.6	39.7	37.9	36.1	33.3	30.4	27.6	24.7	23.3	28.6
97.5°	45.6	43.5	41.4	39.4	37.3	50.5	63.7	77.0	90.2	96.8	100.4
100°	46.8	44.7	42.6	40.6	38.5	78.9	119.3	159.8	200.2	220.4	217.8
102.5°	52.1	60.6	69.2	77.7	86.3	131.4	176.5	221.6	266.7	289.2	287.5
105°	71.9	117.8	163.7	209.5	255.4	278.7	302.0	325.3	348.6	360.3	358.9
107.5°	294.0	333.9	373.8	413.7	453.6	449.7	445.8	441.9	438.0	436.1	434.9
110°	491.7	500.2	508.8	517.3	525.9	523.1	520.2	517.4	514.5	513.1	512.1

TEST NUMBER: P1010636

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	608.7	606.4	604.1	601.7	599.4	596.5	593.7	590.8	587.9	586.5	585.6
115°	679.7	677.1	674.5	671.9	669.3	667.0	664.6	662.3	660.0	658.8	658.0
117.5°	746.5	744.4	742.3	740.2	738.1	736.8	735.5	734.2	732.9	732.3	731.4
120°	812.9	810.8	808.7	806.7	804.6	803.8	803.0	802.3	801.5	801.1	799.9
122.5°	876.3	875.0	873.7	872.4	871.1	870.1	869.0	868.0	866.9	866.4	865.5
125°	934.9	934.4	933.9	933.4	932.9	931.9	930.8	929.8	928.7	928.2	927.2
127.5°	997.8	997.0	996.3	995.5	994.7	993.4	992.1	990.8	989.5	988.8	987.8
130°	1053.6	1052.6	1051.5	1050.5	1049.5	1048.5	1047.4	1046.4	1045.3	1044.8	1043.8
132.5°	1106.1	1105.0	1104.0	1102.9	1101.9	1101.1	1100.3	1099.6	1098.8	1098.4	1097.4
135°	1158.7	1157.9	1157.2	1156.4	1155.6	1154.6	1153.5	1152.5	1151.4	1150.9	1150.1
137.5°	1207.4	1206.1	1204.8	1203.5	1202.2	1201.7	1201.2	1200.7	1200.2	1199.9	1198.9
140°	1251.9	1250.8	1249.8	1248.7	1247.7	1246.9	1246.1	1245.4	1244.6	1244.2	1243.4
142.5°	1293.9	1293.1	1292.4	1291.6	1290.8	1290.0	1289.2	1288.5	1287.7	1287.3	1286.5
145°	1332.5	1332.0	1331.5	1331.0	1330.5	1330.0	1329.5	1329.0	1328.5	1328.2	1327.3
147.5°	1368.7	1368.2	1367.7	1367.1	1366.6	1366.1	1365.6	1365.1	1364.6	1364.3	1363.7
150°	1401.3	1400.8	1400.3	1399.8	1399.3	1398.8	1398.3	1397.8	1397.3	1397.0	1396.6
152.5°	1431.4	1430.4	1429.3	1428.3	1427.3	1427.0	1426.8	1426.5	1426.2	1426.1	1426.0
155°	1458.1	1456.8	1455.5	1454.2	1452.9	1452.7	1452.4	1452.2	1451.9	1451.8	1452.1
157.5°	1482.4	1480.9	1479.4	1477.8	1476.3	1476.5	1476.8	1477.0	1477.3	1477.4	1477.4
160°	1502.3	1500.8	1499.2	1497.7	1496.1	1496.3	1496.6	1496.8	1497.1	1497.2	1497.3
162.5°	1520.8	1519.0	1517.2	1515.4	1513.6	1513.8	1514.1	1514.3	1514.6	1514.7	1515.1
165°	1537.1	1535.0	1532.9	1530.8	1528.7	1529.0	1529.2	1529.5	1529.8	1529.9	1530.3
167.5°	1549.9	1547.8	1545.7	1543.7	1541.6	1541.6	1541.6	1541.6	1541.6	1541.6	1542.1
170°	1560.4	1558.3	1556.2	1554.1	1552.0	1552.0	1552.0	1552.0	1552.0	1552.0	1552.5
172.5°	1567.4	1565.3	1563.2	1561.1	1559.0	1558.8	1558.5	1558.3	1558.0	1557.9	1558.5
175°	1572.1	1570.3	1568.5	1566.7	1564.9	1564.6	1564.4	1564.1	1563.8	1563.7	1564.3
177.5°	1575.5	1573.4	1571.3	1569.3	1567.2	1566.9	1566.7	1566.4	1566.1	1566.0	1566.7
180°	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5	1569.5

TEST NUMBER: P1010636

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	790.5	790.5	790.5	790.5
2.5°	773.7	776.0	783.7	792.8
5°	758.4	764.5	775.2	789.8
7.5°	741.5	750.7	766.0	784.4
10°	722.4	735.4	754.5	777.5
12.5°	701.7	718.5	743.1	766.8
15°	688.7	705.5	727.7	753.8
17.5°	663.4	683.3	706.3	743.1
20°	637.3	659.6	689.4	726.2
22.5°	617.4	641.2	669.5	708.6
25°	593.7	618.2	648.8	689.4
27.5°	568.4	592.9	627.4	670.3
30°	549.2	573.0	605.9	651.9
32.5°	526.3	549.2	583.7	632.0
35°	500.2	526.3	559.2	608.2
37.5°	480.3	504.1	538.5	585.3
40°	458.9	479.5	513.2	559.2
42.5°	435.9	458.9	488.0	533.9
45°	414.4	431.3	461.2	504.8
47.5°	391.4	410.6	433.6	467.3
50°	366.9	383.0	408.3	431.3
52.5°	343.2	356.2	377.7	395.3
55°	317.9	330.9	347.0	357.7
57.5°	294.2	303.3	314.1	321.0
60°	265.0	274.2	281.1	288.0
62.5°	239.0	245.9	249.7	253.6
65°	212.2	216.0	218.3	221.4
67.5°	183.1	186.9	187.7	192.3
70°	156.3	157.0	158.6	160.9
72.5°	131.0	132.5	131.8	133.3
75°	104.9	106.5	104.9	106.5
77.5°	79.7	81.2	81.2	83.5
80°	57.5	58.2	59.0	59.0
82.5°	37.5	39.8	38.3	39.1
85°	21.4	22.2	22.2	23.0
87.5°	10.0	10.7	10.0	11.5
90°	8.9	6.4	3.8	1.2
92.5°	22.1	23.7	25.2	26.8
95°	39.2	49.9	60.5	71.1
97.5°	107.7	114.9	122.2	129.4
100°	212.6	207.5	202.3	197.1
102.5°	284.1	280.8	277.4	274.0
105°	356.0	353.2	350.3	347.5
107.5°	432.6	430.3	427.9	425.6
110°	510.0	507.9	505.8	503.7

TEST NUMBER: P1010636

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	583.8	582.0	580.2	578.4
115°	656.5	654.9	653.4	651.8
117.5°	729.6	727.7	725.9	724.1
120°	797.6	795.3	792.9	790.6
122.5°	863.7	861.8	860.0	858.2
125°	925.1	923.0	921.0	918.9
127.5°	985.7	983.6	981.6	979.5
130°	1041.7	1039.6	1037.6	1035.5
132.5°	1095.3	1093.2	1091.2	1089.1
135°	1148.6	1147.0	1145.5	1143.9
137.5°	1196.8	1194.7	1192.7	1190.6
140°	1241.9	1240.3	1238.8	1237.2
142.5°	1285.0	1283.5	1281.9	1280.4
145°	1325.5	1323.6	1321.8	1320.0
147.5°	1362.4	1361.1	1359.8	1358.5
150°	1395.8	1395.1	1394.3	1393.5
152.5°	1425.7	1425.4	1425.2	1424.9
155°	1452.6	1453.1	1453.6	1454.1
157.5°	1477.4	1477.4	1477.4	1477.4
160°	1497.6	1497.9	1498.1	1498.4
162.5°	1515.9	1516.6	1517.4	1518.2
165°	1531.1	1531.8	1532.6	1533.4
167.5°	1543.1	1544.2	1545.2	1546.2
170°	1553.6	1554.6	1555.7	1556.7
172.5°	1559.8	1561.1	1562.4	1563.7
175°	1565.6	1566.9	1568.2	1569.5
177.5°	1568.0	1569.3	1570.6	1571.9
180°	1569.5	1569.5	1569.5	1569.5

(END OF REPORT)