

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010803

Luminaire Tested: S123RDIP-B1000D585UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010803
REPORT IS A COMBINATION OF REPORTS P992849 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D585UB2750-4F0-XX-W2A-A_5000K
Description: Define 3 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6039.0 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010803

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010803

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	68	68	63
1	101	97	94	90	95	91	88	85	80	78	76	70	69	67	61	60	59	59	59	54
2	93	86	80	75	87	81	76	71	71	67	64	63	60	57	55	53	51	51	51	47
3	85	76	69	63	80	72	65	60	64	59	55	56	52	49	49	46	44	44	44	40
4	78	68	60	54	73	64	57	52	57	52	47	50	46	43	44	41	38	38	38	35
5	72	61	53	47	68	58	50	45	51	46	41	46	41	38	40	37	34	34	34	31
6	67	55	47	41	63	52	45	40	47	41	36	42	37	33	37	33	30	30	30	28
7	62	50	42	37	58	47	40	35	43	37	32	38	33	30	34	30	27	27	27	25
8	58	46	38	33	54	43	36	31	39	33	29	35	30	27	31	27	24	24	24	22
9	54	42	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22	22	22	20
10	50	38	31	26	47	37	30	26	33	28	24	30	25	22	27	23	20	20	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16353	16353	16353	16353
5°	16365	18834	16407	13972
10°	16221	22735	16291	12205
15°	16054	25803	16054	10761
20°	15725	27832	15814	9546
25°	15484	26443	15453	8710
30°	15204	18321	15172	7893
35°	14866	11763	14798	7277
40°	14447	8306	14375	6665
45°	13715	6647	13696	6067
50°	12817	5561	12775	5369
55°	11808	4583	11714	4552
60°	10817	3788	10709	3871
65°	9653	3031	9715	3281
70°	8581	2107	8811	2652
75°	7273	1563	7570	2040
80°	5793	1035	6287	1529
85°	4121	490	4495	951

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 21832 cd/sqm

TEST NUMBER: P1010803

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.2	2.5
10°-20°	467.0	7.7
20°-30°	735.6	12.2
30°-40°	764.9	12.7
40°-50°	654.4	10.8
50°-60°	498.9	8.3
60°-70°	319.6	5.3
70°-80°	153.1	2.5
80°-90°	41.7	0.7
90°-100°	26.1	0.4
100°-110°	126.1	2.1
110°-120°	309.0	5.1
120°-130°	392.2	6.5
130°-140°	419.0	6.9
140°-150°	391.8	6.5
150°-160°	316.0	5.2
160°-170°	204.0	3.4
170°-180°	70.3	1.2
0°-30°	1351.8	22.4
0°-40°	2116.7	35.1
0°-60°	3270.0	54.1
0°-90°	3784.5	62.7
90°-120°	461.2	7.6
90°-150°	1664.2	27.6
90°-180°	2255.0	37.3
0°-180°	6039.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1519	1519	1519	1519	1519	
5°	1518	1804	1522	1338	1518	144
15°	1450	2564	1450	1069	1450	408
25°	1319	2642	1316	870	1319	608
35°	1151	1146	1146	709	1151	720
45°	924	611	922	558	924	711
55°	652	384	646	381	652	584
65°	399	221	402	239	399	399
75°	191	94	199	122	191	206
85°	43	22	47	43	43	48
90°	0	16	0	16	0	4
95°	34	21	34	21	34	40
105°	164	24	164	24	164	174
115°	307	323	307	323	307	303
125°	433	442	433	442	433	387
135°	539	544	539	544	539	415
145°	622	628	622	628	622	389
155°	685	684	685	684	685	316
165°	722	721	722	721	722	204
175°	740	737	740	737	740	70
180°	740	740	740	740	740	

TEST NUMBER: P1010803

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2
2.5°	1523.1	1533.6	1541.4	1546.6	1559.6	1567.4	1573.9	1585.6	1585.6	1588.2	1593.4
5°	1517.9	1540.1	1555.7	1576.5	1603.8	1616.8	1635.0	1650.6	1672.7	1684.4	1696.1
7.5°	1506.2	1537.5	1570.0	1601.2	1641.5	1667.5	1685.7	1726.1	1754.7	1789.8	1817.1
10°	1490.6	1533.6	1575.2	1623.3	1677.9	1717.0	1744.3	1797.6	1852.2	1901.7	1943.3
12.5°	1471.1	1523.1	1583.0	1641.5	1718.3	1757.3	1801.5	1867.8	1945.9	2008.3	2064.2
15°	1450.3	1510.1	1577.8	1649.3	1745.6	1800.2	1863.9	1944.6	2031.7	2121.5	2198.2
17.5°	1417.8	1493.2	1568.7	1672.7	1785.9	1818.4	1873.0	1983.6	2091.6	2172.2	2265.9
20°	1385.3	1469.8	1564.8	1658.4	1780.7	1856.1	1906.9	2023.9	2139.7	2237.2	2327.0
22.5°	1355.4	1443.8	1542.7	1661.0	1775.5	1850.9	1914.7	2036.9	2170.9	2280.2	2390.7
25°	1318.9	1415.2	1524.4	1636.3	1775.5	1832.7	1903.0	2044.7	2186.5	2312.7	2449.3
27.5°	1279.9	1377.5	1485.4	1599.9	1727.4	1811.9	1880.8	2033.0	2206.0	2341.3	2481.8
30°	1240.9	1341.0	1445.1	1547.9	1690.9	1771.6	1850.9	2018.7	2216.4	2371.2	2479.2
32.5°	1203.2	1287.7	1390.5	1490.6	1632.4	1720.9	1810.6	2004.4	2220.3	2350.4	2402.4
35°	1151.1	1239.6	1322.8	1429.5	1572.6	1659.7	1765.1	2003.1	2203.4	2284.1	2258.1
37.5°	1103.0	1177.2	1256.5	1351.5	1498.4	1611.6	1720.9	1969.3	2147.5	2152.7	2005.7
40°	1049.7	1110.8	1177.2	1277.3	1436.0	1547.9	1666.2	1917.3	2046.0	1969.3	1710.4
42.5°	988.5	1043.2	1095.2	1192.8	1365.8	1490.6	1618.1	1852.2	1899.1	1722.2	1452.9
45°	923.5	967.7	1015.9	1118.6	1291.6	1415.2	1542.7	1752.1	1703.9	1454.2	1198.0
47.5°	855.9	893.6	940.4	1034.1	1212.3	1338.4	1459.4	1609.0	1486.7	1218.8	1004.2
50°	788.2	818.2	863.7	959.9	1131.6	1246.1	1358.0	1455.5	1283.8	1045.8	829.9
52.5°	721.9	745.3	792.1	874.1	1040.6	1149.8	1230.5	1268.2	1093.9	863.7	720.6
55°	651.7	677.7	708.9	792.1	957.3	1038.0	1091.3	1090.0	910.5	732.3	595.7
57.5°	584.0	607.4	634.8	718.0	852.0	906.6	952.1	930.0	759.6	599.6	511.2
60°	524.2	537.2	567.1	637.4	738.8	785.6	811.7	773.9	620.4	506.0	422.7
62.5°	459.2	472.2	496.9	563.2	625.6	650.4	672.5	624.3	512.5	412.3	361.6
65°	399.3	416.2	431.8	485.2	519.0	548.9	546.3	506.0	400.6	335.6	294.0
67.5°	347.3	353.8	366.8	399.3	414.9	437.0	438.3	392.8	322.6	273.2	248.4
70°	291.4	297.9	307.0	322.6	333.0	338.2	335.6	295.3	243.2	213.3	191.2
72.5°	243.2	241.9	248.4	248.4	258.8	257.5	249.7	218.5	184.7	160.0	147.0
75°	191.2	192.5	193.8	191.2	187.3	182.1	175.6	152.2	130.1	118.4	106.7
77.5°	149.6	147.0	148.3	139.2	134.0	128.8	119.7	108.0	89.7	87.1	81.9
80°	106.7	105.4	104.1	100.2	88.4	83.2	76.7	70.2	66.3	63.7	62.4
82.5°	71.5	71.5	68.9	61.1	54.6	50.7	49.4	46.8	42.9	42.9	41.6
85°	42.9	41.6	39.0	31.2	27.3	27.3	27.3	27.3	24.7	24.7	23.4
87.5°	16.9	15.6	11.7	11.7	10.4	10.4	10.4	9.1	9.1	7.8	7.8
90°	0.5	1.7	2.9	4.2	5.4	6.0	6.8	8.4	10.0	11.6	13.2
92.5°	12.6	11.9	11.1	10.4	9.7	9.3	9.9	11.0	12.1	13.2	14.3
95°	33.5	28.5	23.5	18.5	13.5	11.0	11.7	13.0	14.3	15.7	17.0
97.5°	61.0	57.6	54.2	50.7	47.3	45.6	42.5	36.3	30.0	23.8	17.6
100°	92.9	95.3	97.7	100.2	102.6	103.8	94.3	75.2	56.2	37.1	18.1
102.5°	129.1	130.7	132.3	133.9	135.5	136.3	125.7	104.4	83.2	61.9	40.7
105°	163.7	165.1	166.4	167.8	169.1	169.8	164.3	153.3	142.3	131.3	120.3
107.5°	200.5	201.6	202.7	203.8	204.9	205.5	206.4	208.2	210.1	211.9	213.7
110°	237.4	238.4	239.3	240.3	241.2	241.7	242.4	243.7	245.1	246.4	247.8

TEST NUMBER: P1010803

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	272.5	273.4	274.2	275.1	276.0	276.4	277.1	278.4	279.7	281.1	282.4
115°	307.1	307.8	308.6	309.3	310.0	310.4	311.0	312.1	313.2	314.3	315.4
117.5°	341.2	342.0	342.9	343.7	344.6	345.0	345.3	345.9	346.6	347.2	347.8
120°	372.5	373.6	374.7	375.8	376.9	377.5	377.7	378.0	378.4	378.7	379.1
122.5°	404.4	405.2	406.1	406.9	407.8	408.2	408.4	408.9	409.4	409.9	410.4
125°	432.9	433.9	434.9	435.8	436.8	437.3	437.5	438.0	438.5	439.0	439.5
127.5°	461.5	462.5	463.5	464.4	465.4	465.9	466.2	466.8	467.5	468.1	468.7
130°	487.9	488.9	489.9	490.8	491.8	492.3	492.5	493.0	493.5	494.0	494.5
132.5°	513.2	514.2	515.2	516.1	517.1	517.6	517.8	518.1	518.5	518.8	519.2
135°	539.0	539.7	540.5	541.2	541.9	542.3	542.5	543.0	543.5	544.0	544.5
137.5°	561.0	562.0	563.0	563.9	564.9	565.4	565.5	565.8	566.0	566.3	566.5
140°	582.9	583.6	584.4	585.1	585.8	586.2	586.4	586.8	587.1	587.5	587.9
142.5°	603.3	604.0	604.8	605.5	606.2	606.6	606.8	607.1	607.5	607.8	608.2
145°	622.0	622.8	623.7	624.5	625.4	625.8	625.9	626.2	626.4	626.7	626.9
147.5°	640.1	640.7	641.3	641.9	642.5	642.8	642.9	643.2	643.4	643.7	643.9
150°	656.6	657.0	657.3	657.7	658.0	658.2	658.3	658.6	658.8	659.1	659.3
152.5°	671.4	671.5	671.7	671.8	671.9	672.0	672.1	672.2	672.3	672.4	672.5
155°	685.1	684.9	684.6	684.4	684.1	684.0	684.1	684.2	684.3	684.5	684.6
157.5°	696.1	696.1	696.1	696.1	696.1	696.1	696.0	695.9	695.8	695.7	695.6
160°	706.0	705.9	705.8	705.7	705.6	705.5	705.4	705.3	705.2	705.0	704.9
162.5°	715.4	715.0	714.6	714.3	713.9	713.7	713.6	713.5	713.4	713.3	713.2
165°	722.5	722.1	721.8	721.4	721.1	720.9	720.8	720.7	720.6	720.4	720.3
167.5°	728.5	728.0	727.5	727.0	726.5	726.3	726.3	726.3	726.3	726.3	726.3
170°	733.5	733.0	732.5	732.0	731.5	731.3	731.3	731.3	731.3	731.3	731.3
172.5°	736.8	736.2	735.6	734.9	734.3	734.0	734.1	734.2	734.3	734.5	734.6
175°	739.5	738.9	738.3	737.7	737.1	736.8	736.9	737.0	737.1	737.2	737.3
177.5°	740.6	740.0	739.4	738.8	738.2	737.9	738.0	738.1	738.2	738.3	738.4
180°	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5

TEST NUMBER: P1010803

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2
2.5°	1603.8	1603.8	1615.5	1627.2	1620.7	1624.6	1638.9	1633.7	1644.1	1642.8	1646.7
5°	1724.8	1739.1	1750.8	1775.5	1779.4	1775.5	1800.2	1806.7	1818.4	1804.1	1810.6
7.5°	1861.3	1891.2	1919.9	1956.3	1968.0	1970.6	1983.6	2001.8	2017.4	1988.8	2003.1
10°	1994.0	2039.5	2098.1	2130.6	2159.2	2169.6	2180.0	2191.7	2209.9	2226.8	2213.8
12.5°	2137.1	2203.4	2259.4	2317.9	2353.0	2349.1	2379.0	2386.8	2401.1	2405.0	2410.2
15°	2254.2	2347.8	2382.9	2470.1	2477.9	2503.9	2537.7	2567.6	2571.5	2563.7	2563.7
17.5°	2366.0	2446.7	2509.1	2579.3	2593.6	2615.8	2658.7	2673.0	2678.2	2676.9	2676.9
20°	2457.1	2510.4	2615.8	2674.3	2697.7	2726.3	2756.2	2774.4	2778.3	2783.5	2775.7
22.5°	2516.9	2597.5	2683.4	2731.5	2751.0	2761.4	2780.9	2786.1	2779.6	2780.9	2782.2
25°	2563.7	2643.1	2695.1	2708.1	2706.8	2693.8	2679.5	2654.8	2652.2	2641.8	2621.0
27.5°	2576.7	2606.6	2600.1	2546.8	2493.5	2488.3	2402.4	2355.6	2302.3	2310.1	2280.2
30°	2506.5	2467.5	2375.1	2239.8	2183.9	2092.9	1996.6	1896.5	1857.4	1814.5	1893.9
32.5°	2334.8	2195.6	2031.7	1856.1	1762.5	1681.8	1579.1	1506.2	1464.6	1429.5	1497.1
35°	2076.0	1858.7	1641.5	1475.0	1398.3	1325.4	1229.2	1192.8	1140.7	1145.9	1152.4
37.5°	1743.0	1503.6	1339.7	1175.9	1125.1	1095.2	1025.0	969.0	950.8	945.6	945.6
40°	1430.8	1234.4	1088.7	959.9	920.9	896.2	840.3	814.3	794.7	789.5	796.0
42.5°	1183.7	1015.9	902.7	816.9	789.5	758.3	734.9	702.4	698.5	689.4	701.1
45°	993.8	848.1	763.5	701.1	677.7	666.0	640.0	620.4	612.6	611.3	620.4
47.5°	842.9	729.7	655.6	616.5	598.3	586.6	564.5	556.7	548.9	551.5	547.6
50°	707.6	623.0	574.9	539.8	528.1	516.4	502.1	494.3	490.4	490.4	489.1
52.5°	607.4	537.2	506.0	473.5	468.3	461.8	446.1	440.9	434.4	433.1	438.3
55°	520.3	472.2	440.9	421.4	416.2	403.2	396.7	390.2	386.3	383.7	385.0
57.5°	444.8	408.4	387.6	370.7	361.6	356.4	344.7	343.4	340.8	340.8	339.5
60°	382.4	356.4	331.7	321.3	314.8	308.3	307.0	299.2	295.3	297.9	296.6
62.5°	323.9	303.1	288.8	277.1	273.2	267.9	264.0	261.4	257.5	258.8	258.8
65°	270.6	253.6	243.2	232.8	231.5	226.3	225.0	222.4	222.4	221.1	223.7
67.5°	222.4	210.7	201.6	195.1	191.2	192.5	187.3	183.4	183.4	182.1	186.0
70°	176.9	170.4	161.3	153.5	148.3	148.3	141.8	140.5	140.5	140.5	139.2
72.5°	136.6	124.9	121.0	118.4	118.4	118.4	115.8	115.8	114.5	115.8	114.5
75°	101.5	100.2	97.6	96.3	96.3	95.0	93.7	93.7	93.7	93.7	93.7
77.5°	79.3	79.3	76.7	75.4	75.4	75.4	74.1	74.1	72.8	72.8	72.8
80°	58.5	58.5	55.9	55.9	55.9	54.6	54.6	54.6	55.9	54.6	54.6
82.5°	40.3	40.3	39.0	40.3	39.0	37.7	37.7	37.7	36.4	37.7	37.7
85°	23.4	23.4	22.1	20.8	22.1	22.1	20.8	22.1	20.8	22.1	20.8
87.5°	9.1	7.8	7.8	7.8	6.5	7.8	6.5	6.5	7.8	6.5	7.8
90°	13.7	14.2	14.7	15.2	15.4	15.5	15.8	16.0	16.3	16.5	16.3
92.5°	15.1	16.0	16.8	17.7	18.1	18.2	18.3	18.4	18.6	18.7	18.6
95°	17.9	18.7	19.6	20.5	20.9	20.9	20.9	20.9	20.9	20.9	20.9
97.5°	18.6	19.6	20.5	21.5	22.0	22.1	22.2	22.3	22.4	22.5	22.4
100°	19.1	20.1	21.0	22.0	22.5	22.6	22.7	22.8	23.0	23.1	23.0
102.5°	36.7	32.6	28.6	24.5	22.5	22.6	22.9	23.1	23.4	23.6	23.4
105°	98.7	77.1	55.5	33.9	23.1	23.2	23.5	23.7	24.0	24.2	24.0
107.5°	194.9	176.1	157.3	138.5	129.1	121.1	105.1	89.1	73.1	57.1	73.1
110°	243.8	239.8	235.7	231.7	229.7	221.0	203.5	186.0	168.6	151.1	168.6

TEST NUMBER: P1010803

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	283.5	284.6	285.7	286.8	287.4	287.3	287.0	286.8	286.5	286.3	286.5
115°	316.6	317.8	319.1	320.3	320.9	321.1	321.6	322.1	322.6	323.1	322.6
117.5°	348.8	349.8	350.7	351.7	352.2	352.3	352.4	352.5	352.6	352.7	352.6
120°	380.1	381.1	382.0	383.0	383.5	383.5	383.5	383.5	383.5	383.5	383.5
122.5°	411.0	411.6	412.3	412.9	413.2	413.3	413.4	413.5	413.6	413.7	413.6
125°	439.7	440.0	440.2	440.5	440.6	440.7	441.0	441.2	441.5	441.7	441.5
127.5°	469.1	469.4	469.8	470.1	470.3	470.2	469.9	469.7	469.4	469.2	469.4
130°	495.0	495.5	496.0	496.5	496.7	496.6	496.3	496.1	495.8	495.6	495.8
132.5°	519.7	520.2	520.7	521.2	521.4	521.2	520.9	520.5	520.2	519.8	520.2
135°	544.9	545.2	545.6	545.9	546.1	545.9	545.6	545.2	544.9	544.5	544.9
137.5°	567.1	567.7	568.3	568.9	569.2	569.1	568.8	568.6	568.3	568.1	568.3
140°	588.4	588.9	589.4	589.9	590.1	590.0	589.7	589.5	589.2	589.0	589.2
142.5°	608.6	609.0	609.3	609.7	609.9	609.7	609.3	609.0	608.6	608.2	608.6
145°	627.1	627.4	627.6	627.9	628.0	628.0	628.0	628.0	628.0	628.0	628.0
147.5°	644.1	644.4	644.6	644.9	645.0	644.7	644.1	643.5	642.9	642.3	642.9
150°	659.5	659.8	660.0	660.3	660.4	660.2	659.9	659.5	659.2	658.8	659.2
152.5°	673.0	673.5	674.0	674.5	674.7	674.4	673.8	673.2	672.6	672.0	672.6
155°	685.2	685.8	686.4	687.0	687.3	686.9	686.2	685.5	684.7	684.0	684.7
157.5°	696.3	697.1	697.8	698.5	698.9	698.4	697.4	696.5	695.5	694.5	695.5
160°	705.6	706.4	707.1	707.8	708.2	707.8	706.9	706.1	705.2	704.4	705.2
162.5°	714.0	714.9	715.7	716.6	717.0	716.6	715.9	715.2	714.4	713.7	714.4
165°	721.3	722.3	723.2	724.2	724.7	724.3	723.4	722.6	721.7	720.9	721.7
167.5°	727.3	728.3	729.2	730.2	730.7	730.2	729.2	728.3	727.3	726.3	727.3
170°	732.3	733.3	734.2	735.2	735.7	735.2	734.2	733.3	732.3	731.3	732.3
172.5°	735.6	736.6	737.5	738.5	739.0	738.4	737.3	736.2	735.1	734.0	735.1
175°	738.2	739.0	739.9	740.8	741.2	740.7	739.7	738.8	737.8	736.8	737.8
177.5°	739.4	740.4	741.3	742.3	742.8	742.2	741.0	739.7	738.5	737.3	738.5
180°	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5

TEST NUMBER: P1010803

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2
2.5°	1640.2	1632.4	1627.2	1623.3	1619.4	1631.1	1615.5	1598.6	1586.9	1579.1	1576.5
5°	1811.9	1795.0	1780.7	1769.0	1771.6	1771.6	1744.3	1714.4	1688.3	1674.0	1658.4
7.5°	2010.9	1992.7	1964.1	1957.6	1952.4	1919.9	1892.6	1837.9	1805.4	1772.9	1744.3
10°	2208.6	2185.2	2157.9	2148.8	2135.8	2095.5	2053.8	1983.6	1943.3	1883.4	1845.7
12.5°	2393.3	2364.7	2337.4	2330.9	2311.4	2276.3	2204.7	2131.9	2062.9	1999.2	1932.9
15°	2548.1	2540.3	2498.7	2472.7	2429.7	2381.6	2366.0	2267.2	2180.0	2113.7	1994.0
17.5°	2678.2	2641.8	2602.7	2585.8	2568.9	2513.0	2457.1	2355.6	2262.0	2164.4	2087.7
20°	2782.2	2741.9	2714.6	2689.9	2682.1	2618.4	2529.9	2440.2	2337.4	2228.1	2128.0
22.5°	2787.4	2782.2	2764.0	2749.7	2734.1	2692.5	2622.3	2510.4	2401.1	2281.5	2150.1
25°	2679.5	2671.7	2723.7	2710.7	2721.1	2705.5	2667.8	2574.1	2446.7	2306.2	2173.5
27.5°	2354.3	2433.7	2515.6	2544.2	2563.7	2619.7	2637.9	2585.8	2483.1	2333.5	2185.2
30°	1912.1	2017.4	2150.1	2221.6	2276.3	2380.3	2515.6	2532.5	2484.4	2364.7	2182.6
32.5°	1501.0	1597.3	1703.9	1788.5	1861.3	2074.7	2256.8	2388.1	2411.5	2349.1	2189.1
35°	1209.7	1251.3	1352.8	1433.4	1532.3	1714.4	1929.0	2141.0	2284.1	2291.9	2169.6
37.5°	997.7	1019.8	1108.2	1153.7	1212.3	1372.3	1572.6	1849.6	2072.1	2177.4	2115.0
40°	826.0	876.7	927.4	953.4	995.1	1105.6	1298.1	1515.3	1791.1	1986.2	2030.4
42.5°	716.7	738.8	771.3	807.7	833.8	930.0	1058.8	1257.8	1506.2	1778.1	1900.4
45°	632.2	640.0	673.8	697.2	724.5	792.1	883.2	1049.7	1268.2	1536.2	1744.3
47.5°	561.9	577.5	595.7	610.0	628.2	680.3	758.3	879.3	1071.8	1311.1	1534.9
50°	499.5	508.6	532.0	538.5	551.5	587.9	647.8	740.1	898.8	1090.0	1321.5
52.5°	440.9	457.9	467.0	476.1	487.8	517.7	556.7	632.2	751.8	931.3	1127.7
55°	395.4	400.6	413.6	421.4	430.5	451.4	485.2	541.1	634.8	777.8	963.8
57.5°	351.2	351.2	364.2	370.7	379.8	395.4	425.3	468.3	535.9	642.6	813.0
60°	304.4	305.7	316.1	323.9	326.5	342.1	366.8	400.6	452.7	530.7	669.9
62.5°	262.7	269.2	274.5	277.1	286.2	295.3	316.1	339.5	375.9	444.8	543.7
65°	227.6	228.9	232.8	235.4	239.3	249.7	265.3	281.0	312.2	362.9	443.5
67.5°	187.3	192.5	197.7	197.7	201.6	206.8	222.4	235.4	258.8	288.8	343.4
70°	140.5	143.1	150.9	154.8	160.0	169.1	176.9	184.7	202.9	225.0	266.6
72.5°	117.1	117.1	119.7	121.0	121.0	127.5	139.2	147.0	156.1	171.7	200.3
75°	93.7	93.7	97.6	96.3	98.9	101.5	102.8	108.0	113.2	124.9	141.8
77.5°	74.1	75.4	75.4	76.7	76.7	78.0	79.3	81.9	84.5	91.1	98.9
80°	54.6	55.9	55.9	57.2	57.2	58.5	59.8	61.1	63.7	66.3	70.2
82.5°	37.7	39.0	39.0	40.3	39.0	40.3	41.6	41.6	42.9	45.5	46.8
85°	22.1	22.1	23.4	22.1	22.1	22.1	23.4	23.4	24.7	28.6	28.6
87.5°	6.5	7.8	6.5	7.8	7.8	7.8	7.8	9.1	9.1	10.4	11.7
90°	16.0	15.8	15.5	15.4	15.2	14.7	14.2	13.7	13.2	11.6	10.0
92.5°	18.4	18.3	18.2	18.1	17.7	16.8	16.0	15.1	14.3	13.2	12.1
95°	20.9	20.9	20.9	20.9	20.5	19.6	18.7	17.9	17.0	15.7	14.3
97.5°	22.3	22.2	22.1	22.0	21.5	20.5	19.6	18.6	17.6	23.8	30.0
100°	22.8	22.7	22.6	22.5	22.0	21.0	20.1	19.1	18.1	37.1	56.2
102.5°	23.1	22.9	22.6	22.5	24.5	28.6	32.6	36.7	40.7	61.9	83.2
105°	23.7	23.5	23.2	23.1	33.9	55.5	77.1	98.7	120.3	131.3	142.3
107.5°	89.1	105.1	121.1	129.1	138.5	157.3	176.1	194.9	213.7	211.9	210.1
110°	186.0	203.5	221.0	229.7	231.7	235.7	239.8	243.8	247.8	246.4	245.1

TEST NUMBER: P1010803

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	286.8	287.0	287.3	287.4	286.8	285.7	284.6	283.5	282.4	281.1	279.7
115°	322.1	321.6	321.1	320.9	320.3	319.1	317.8	316.6	315.4	314.3	313.2
117.5°	352.5	352.4	352.3	352.2	351.7	350.7	349.8	348.8	347.8	347.2	346.6
120°	383.5	383.5	383.5	383.5	383.0	382.0	381.1	380.1	379.1	378.7	378.4
122.5°	413.5	413.4	413.3	413.2	412.9	412.3	411.6	411.0	410.4	409.9	409.4
125°	441.2	441.0	440.7	440.6	440.5	440.2	440.0	439.7	439.5	439.0	438.5
127.5°	469.7	469.9	470.2	470.3	470.1	469.8	469.4	469.1	468.7	468.1	467.5
130°	496.1	496.3	496.6	496.7	496.5	496.0	495.5	495.0	494.5	494.0	493.5
132.5°	520.5	520.9	521.2	521.4	521.2	520.7	520.2	519.7	519.2	518.8	518.5
135°	545.2	545.6	545.9	546.1	545.9	545.6	545.2	544.9	544.5	544.0	543.5
137.5°	568.6	568.8	569.1	569.2	568.9	568.3	567.7	567.1	566.5	566.3	566.0
140°	589.5	589.7	590.0	590.1	589.9	589.4	588.9	588.4	587.9	587.5	587.1
142.5°	609.0	609.3	609.7	609.9	609.7	609.3	609.0	608.6	608.2	607.8	607.5
145°	628.0	628.0	628.0	628.0	627.9	627.6	627.4	627.1	626.9	626.7	626.4
147.5°	643.5	644.1	644.7	645.0	644.9	644.6	644.4	644.1	643.9	643.7	643.4
150°	659.5	659.9	660.2	660.4	660.3	660.0	659.8	659.5	659.3	659.1	658.8
152.5°	673.2	673.8	674.4	674.7	674.5	674.0	673.5	673.0	672.5	672.4	672.3
155°	685.5	686.2	686.9	687.3	687.0	686.4	685.8	685.2	684.6	684.5	684.3
157.5°	696.5	697.4	698.4	698.9	698.5	697.8	697.1	696.3	695.6	695.7	695.8
160°	706.1	706.9	707.8	708.2	707.8	707.1	706.4	705.6	704.9	705.0	705.2
162.5°	715.2	715.9	716.6	717.0	716.6	715.7	714.9	714.0	713.2	713.3	713.4
165°	722.6	723.4	724.3	724.7	724.2	723.2	722.3	721.3	720.3	720.4	720.6
167.5°	728.3	729.2	730.2	730.7	730.2	729.2	728.3	727.3	726.3	726.3	726.3
170°	733.3	734.2	735.2	735.7	735.2	734.2	733.3	732.3	731.3	731.3	731.3
172.5°	736.2	737.3	738.4	739.0	738.5	737.5	736.6	735.6	734.6	734.5	734.3
175°	738.8	739.7	740.7	741.2	740.8	739.9	739.0	738.2	737.3	737.2	737.1
177.5°	739.7	741.0	742.2	742.8	742.3	741.3	740.4	739.4	738.4	738.3	738.2
180°	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5

TEST NUMBER: P1010803

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2
2.5°	1572.6	1566.1	1559.6	1559.6	1545.3	1532.3	1525.7	1528.3	1520.5	1510.1	1499.7
5°	1641.5	1615.5	1610.3	1596.0	1576.5	1549.2	1534.9	1521.8	1506.2	1485.4	1465.9
7.5°	1705.2	1671.4	1653.2	1638.9	1601.2	1563.5	1532.3	1511.4	1484.1	1452.9	1429.5
10°	1788.5	1726.1	1706.5	1674.0	1620.7	1567.4	1530.9	1497.1	1459.4	1423.0	1391.8
12.5°	1854.8	1783.3	1746.9	1714.4	1645.4	1577.8	1516.6	1475.0	1429.5	1389.2	1348.8
15°	1930.3	1849.6	1785.9	1746.9	1659.7	1577.8	1508.8	1450.3	1399.6	1350.1	1315.0
17.5°	1966.7	1865.2	1836.6	1780.7	1654.5	1572.6	1488.0	1425.6	1364.5	1307.2	1265.6
20°	2023.9	1905.6	1834.0	1796.3	1684.4	1563.5	1464.6	1393.1	1329.3	1268.2	1224.0
22.5°	2027.8	1899.1	1852.2	1780.7	1642.8	1536.2	1443.8	1356.7	1282.5	1225.3	1179.8
25°	2018.7	1887.3	1822.3	1765.1	1650.6	1520.5	1402.2	1316.3	1243.5	1177.2	1123.8
27.5°	2014.8	1853.5	1792.4	1735.2	1606.4	1475.0	1377.5	1279.9	1196.7	1138.1	1083.5
30°	2009.6	1817.1	1743.0	1676.6	1558.3	1439.9	1322.8	1238.3	1158.9	1084.8	1030.2
32.5°	1975.8	1767.7	1692.2	1622.0	1494.5	1376.2	1283.8	1194.1	1108.2	1039.3	989.8
35°	1965.4	1722.2	1623.3	1547.9	1423.0	1317.6	1220.1	1145.9	1065.3	996.4	937.8
37.5°	1935.5	1675.3	1568.7	1472.4	1342.3	1242.2	1170.6	1096.5	1018.5	944.3	897.5
40°	1883.4	1620.7	1499.7	1400.9	1266.9	1165.4	1099.1	1044.5	967.7	901.4	844.2
42.5°	1806.7	1564.8	1434.7	1330.6	1182.4	1087.4	1032.8	980.7	915.7	846.8	799.9
45°	1718.3	1490.6	1369.7	1253.9	1103.0	1010.7	953.4	922.2	862.4	803.8	749.2
47.5°	1597.3	1413.9	1294.2	1174.6	1021.1	931.3	885.8	854.6	813.0	749.2	705.0
50°	1445.1	1315.0	1201.9	1095.2	940.4	854.6	809.0	785.6	750.5	705.0	662.1
52.5°	1276.0	1200.6	1106.9	1008.1	858.5	777.8	736.2	718.0	692.0	649.1	612.6
55°	1105.6	1073.1	1009.4	911.8	772.6	706.3	669.9	646.5	626.9	595.7	564.5
57.5°	953.4	937.8	893.6	818.2	701.1	632.2	600.9	585.3	569.7	546.3	515.1
60°	796.0	813.0	767.4	729.7	623.0	563.2	535.9	519.0	511.2	490.4	470.9
62.5°	659.5	675.1	649.1	620.4	545.0	491.7	474.8	459.2	454.0	435.7	416.2
65°	535.9	555.4	535.9	520.3	474.8	430.5	409.7	401.9	396.7	385.0	369.4
67.5°	426.6	446.1	437.0	417.5	403.2	366.8	355.1	347.3	344.7	335.6	322.6
70°	321.3	348.6	351.2	339.5	326.5	309.6	301.8	299.2	292.7	284.9	277.1
72.5°	231.5	262.7	264.0	264.0	256.2	256.2	248.4	244.5	244.5	236.7	227.6
75°	170.4	191.2	193.8	196.4	200.3	204.2	199.0	199.0	197.7	189.9	186.0
77.5°	113.2	131.4	137.9	147.0	152.2	152.2	154.8	157.4	154.8	150.9	148.3
80°	72.8	85.8	93.7	98.9	106.7	110.6	114.5	115.8	113.2	111.9	108.0
82.5°	48.1	52.0	55.9	62.4	71.5	78.0	78.0	76.7	79.3	78.0	76.7
85°	27.3	29.9	31.2	32.5	37.7	44.2	45.5	46.8	49.4	46.8	44.2
87.5°	10.4	11.7	11.7	11.7	14.3	15.6	19.5	24.7	23.4	20.8	20.8
90°	8.4	6.8	6.0	5.4	4.2	2.9	1.7	0.5	1.7	2.9	4.2
92.5°	11.0	9.9	9.3	9.7	10.4	11.1	11.9	12.6	11.9	11.1	10.4
95°	13.0	11.7	11.0	13.5	18.5	23.5	28.5	33.5	28.5	23.5	18.5
97.5°	36.3	42.5	45.6	47.3	50.7	54.2	57.6	61.0	57.6	54.2	50.7
100°	75.2	94.3	103.8	102.6	100.2	97.7	95.3	92.9	95.3	97.7	100.2
102.5°	104.4	125.7	136.3	135.5	133.9	132.3	130.7	129.1	130.7	132.3	133.9
105°	153.3	164.3	169.8	169.1	167.8	166.4	165.1	163.7	165.1	166.4	167.8
107.5°	208.2	206.4	205.5	204.9	203.8	202.7	201.6	200.5	201.6	202.7	203.8
110°	243.7	242.4	241.7	241.2	240.3	239.3	238.4	237.4	238.4	239.3	240.3

TEST NUMBER: P1010803

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	278.4	277.1	276.4	276.0	275.1	274.2	273.4	272.5	273.4	274.2	275.1
115°	312.1	311.0	310.4	310.0	309.3	308.6	307.8	307.1	307.8	308.6	309.3
117.5°	345.9	345.3	345.0	344.6	343.7	342.9	342.0	341.2	342.0	342.9	343.7
120°	378.0	377.7	377.5	376.9	375.8	374.7	373.6	372.5	373.6	374.7	375.8
122.5°	408.9	408.4	408.2	407.8	406.9	406.1	405.2	404.4	405.2	406.1	406.9
125°	438.0	437.5	437.3	436.8	435.8	434.9	433.9	432.9	433.9	434.9	435.8
127.5°	466.8	466.2	465.9	465.4	464.4	463.5	462.5	461.5	462.5	463.5	464.4
130°	493.0	492.5	492.3	491.8	490.8	489.9	488.9	487.9	488.9	489.9	490.8
132.5°	518.1	517.8	517.6	517.1	516.1	515.2	514.2	513.2	514.2	515.2	516.1
135°	543.0	542.5	542.3	541.9	541.2	540.5	539.7	539.0	539.7	540.5	541.2
137.5°	565.8	565.5	565.4	564.9	563.9	563.0	562.0	561.0	562.0	563.0	563.9
140°	586.8	586.4	586.2	585.8	585.1	584.4	583.6	582.9	583.6	584.4	585.1
142.5°	607.1	606.8	606.6	606.2	605.5	604.8	604.0	603.3	604.0	604.8	605.5
145°	626.2	625.9	625.8	625.4	624.5	623.7	622.8	622.0	622.8	623.7	624.5
147.5°	643.2	642.9	642.8	642.5	641.9	641.3	640.7	640.1	640.7	641.3	641.9
150°	658.6	658.3	658.2	658.0	657.7	657.3	657.0	656.6	657.0	657.3	657.7
152.5°	672.2	672.1	672.0	671.9	671.8	671.7	671.5	671.4	671.5	671.7	671.8
155°	684.2	684.1	684.0	684.1	684.4	684.6	684.9	685.1	684.9	684.6	684.4
157.5°	695.9	696.0	696.1	696.1	696.1	696.1	696.1	696.1	696.1	696.1	696.1
160°	705.3	705.4	705.5	705.6	705.7	705.8	705.9	706.0	705.9	705.8	705.7
162.5°	713.5	713.6	713.7	713.9	714.3	714.6	715.0	715.4	715.0	714.6	714.3
165°	720.7	720.8	720.9	721.1	721.4	721.8	722.1	722.5	722.1	721.8	721.4
167.5°	726.3	726.3	726.3	726.5	727.0	727.5	728.0	728.5	728.0	727.5	727.0
170°	731.3	731.3	731.3	731.5	732.0	732.5	733.0	733.5	733.0	732.5	732.0
172.5°	734.2	734.1	734.0	734.3	734.9	735.6	736.2	736.8	736.2	735.6	734.9
175°	737.0	736.9	736.8	737.1	737.7	738.3	738.9	739.5	738.9	738.3	737.7
177.5°	738.1	738.0	737.9	738.2	738.8	739.4	740.0	740.6	740.0	739.4	738.8
180°	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5

TEST NUMBER: P1010803

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2
2.5°	1499.7	1493.2	1490.6	1484.1	1468.5	1458.1	1446.4	1438.6	1439.9	1433.4	1437.3
5°	1452.9	1451.6	1442.5	1429.5	1407.4	1395.7	1374.9	1364.5	1359.3	1360.6	1352.8
7.5°	1413.9	1402.2	1395.7	1374.9	1354.1	1329.3	1312.4	1303.3	1295.5	1287.7	1282.5
10°	1369.7	1359.3	1348.8	1326.7	1298.1	1274.7	1251.3	1242.2	1230.5	1225.3	1221.4
12.5°	1322.8	1316.3	1303.3	1277.3	1244.8	1222.7	1195.4	1190.2	1174.6	1164.1	1161.5
15°	1279.9	1276.0	1252.6	1222.7	1190.2	1168.0	1144.6	1129.0	1103.0	1108.2	1099.1
17.5°	1234.4	1217.5	1203.2	1162.8	1147.2	1113.4	1086.1	1078.3	1060.1	1048.4	1036.7
20°	1183.7	1173.3	1155.0	1129.0	1091.3	1052.3	1031.5	1018.5	1008.1	989.8	984.6
22.5°	1135.5	1122.5	1106.9	1073.1	1040.6	1008.1	979.4	967.7	954.7	941.7	933.9
25°	1097.8	1078.3	1061.4	1019.8	987.2	959.9	941.7	922.2	904.0	896.2	893.6
27.5°	1039.3	1027.6	1010.7	971.6	941.7	911.8	894.9	881.9	862.4	853.3	845.5
30°	1001.6	978.1	958.6	927.4	897.5	865.0	849.4	833.8	822.1	810.3	801.2
32.5°	950.8	932.6	917.0	885.8	855.9	826.0	809.0	785.6	779.1	770.0	759.6
35°	901.4	889.7	872.8	839.0	806.4	785.6	767.4	745.3	737.5	731.0	721.9
37.5°	854.6	837.7	826.0	793.4	764.8	740.1	725.8	707.6	702.4	694.6	688.1
40°	814.3	797.3	785.6	753.1	723.2	697.2	688.1	669.9	662.1	653.0	649.1
42.5°	768.7	754.4	738.8	715.4	684.2	658.2	640.0	629.5	619.1	615.2	607.4
45°	720.6	707.6	695.9	669.9	637.4	619.1	603.5	589.2	581.4	574.9	569.7
47.5°	679.0	667.3	651.7	623.0	597.0	580.1	564.5	550.2	542.4	534.6	528.1
50°	630.9	624.3	607.4	580.1	555.4	535.9	521.6	508.6	503.4	494.3	483.9
52.5°	587.9	576.2	561.9	539.8	517.7	494.3	474.8	467.0	457.9	452.7	443.5
55°	537.2	529.4	513.8	494.3	470.9	451.4	437.0	426.6	414.9	409.7	398.0
57.5°	494.3	480.0	472.2	447.4	425.3	405.8	395.4	385.0	372.0	364.2	359.0
60°	447.4	434.4	422.7	401.9	386.3	365.5	349.9	340.8	331.7	321.3	316.1
62.5°	401.9	391.5	377.2	360.3	340.8	323.9	312.2	299.2	294.0	283.6	279.7
65°	352.5	344.7	333.0	313.5	297.9	283.6	271.9	261.4	256.2	252.3	249.7
67.5°	308.3	297.9	290.1	273.2	256.2	244.5	238.0	231.5	225.0	221.1	217.2
70°	262.7	254.9	247.1	231.5	219.8	209.4	204.2	199.0	195.1	191.2	187.3
72.5°	215.9	212.0	204.2	193.8	184.7	176.9	173.0	166.5	162.6	156.1	153.5
75°	178.2	171.7	167.8	158.7	150.9	144.4	139.2	131.4	126.2	123.6	122.3
77.5°	140.5	137.9	132.7	124.9	121.0	114.5	106.7	104.1	101.5	101.5	100.2
80°	105.4	101.5	97.6	91.1	87.1	81.9	81.9	81.9	80.6	81.9	80.6
82.5°	71.5	68.9	66.3	62.4	61.1	61.1	62.4	62.4	62.4	62.4	62.4
85°	41.6	41.6	41.6	42.9	41.6	41.6	42.9	44.2	42.9	42.9	41.6
87.5°	19.5	19.5	20.8	20.8	22.1	22.1	22.1	22.1	22.1	22.1	23.4
90°	5.4	6.0	6.8	8.4	10.0	11.6	13.2	13.7	14.2	14.7	15.2
92.5°	9.7	9.3	9.9	11.0	12.1	13.2	14.3	15.1	16.0	16.8	17.7
95°	13.5	11.0	11.7	13.0	14.3	15.7	17.0	17.9	18.7	19.6	20.5
97.5°	47.3	45.6	42.5	36.3	30.0	23.8	17.6	18.6	19.6	20.5	21.5
100°	102.6	103.8	94.3	75.2	56.2	37.1	18.1	19.1	20.1	21.0	22.0
102.5°	135.5	136.3	125.7	104.4	83.2	61.9	40.7	36.7	32.6	28.6	24.5
105°	169.1	169.8	164.3	153.3	142.3	131.3	120.3	98.7	77.1	55.5	33.9
107.5°	204.9	205.5	206.4	208.2	210.1	211.9	213.7	194.9	176.1	157.3	138.5
110°	241.2	241.7	242.4	243.7	245.1	246.4	247.8	243.8	239.8	235.7	231.7

TEST NUMBER: P1010803

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	276.0	276.4	277.1	278.4	279.7	281.1	282.4	283.5	284.6	285.7	286.8
115°	310.0	310.4	311.0	312.1	313.2	314.3	315.4	316.6	317.8	319.1	320.3
117.5°	344.6	345.0	345.3	345.9	346.6	347.2	347.8	348.8	349.8	350.7	351.7
120°	376.9	377.5	377.7	378.0	378.4	378.7	379.1	380.1	381.1	382.0	383.0
122.5°	407.8	408.2	408.4	408.9	409.4	409.9	410.4	411.0	411.6	412.3	412.9
125°	436.8	437.3	437.5	438.0	438.5	439.0	439.5	439.7	440.0	440.2	440.5
127.5°	465.4	465.9	466.2	466.8	467.5	468.1	468.7	469.1	469.4	469.8	470.1
130°	491.8	492.3	492.5	493.0	493.5	494.0	494.5	495.0	495.5	496.0	496.5
132.5°	517.1	517.6	517.8	518.1	518.5	518.8	519.2	519.7	520.2	520.7	521.2
135°	541.9	542.3	542.5	543.0	543.5	544.0	544.5	544.9	545.2	545.6	545.9
137.5°	564.9	565.4	565.5	565.8	566.0	566.3	566.5	567.1	567.7	568.3	568.9
140°	585.8	586.2	586.4	586.8	587.1	587.5	587.9	588.4	588.9	589.4	589.9
142.5°	606.2	606.6	606.8	607.1	607.5	607.8	608.2	608.6	609.0	609.3	609.7
145°	625.4	625.8	625.9	626.2	626.4	626.7	626.9	627.1	627.4	627.6	627.9
147.5°	642.5	642.8	642.9	643.2	643.4	643.7	643.9	644.1	644.4	644.6	644.9
150°	658.0	658.2	658.3	658.6	658.8	659.1	659.3	659.5	659.8	660.0	660.3
152.5°	671.9	672.0	672.1	672.2	672.3	672.4	672.5	673.0	673.5	674.0	674.5
155°	684.1	684.0	684.1	684.2	684.3	684.5	684.6	685.2	685.8	686.4	687.0
157.5°	696.1	696.1	696.0	695.9	695.8	695.7	695.6	696.3	697.1	697.8	698.5
160°	705.6	705.5	705.4	705.3	705.2	705.0	704.9	705.6	706.4	707.1	707.8
162.5°	713.9	713.7	713.6	713.5	713.4	713.3	713.2	714.0	714.9	715.7	716.6
165°	721.1	720.9	720.8	720.7	720.6	720.4	720.3	721.3	722.3	723.2	724.2
167.5°	726.5	726.3	726.3	726.3	726.3	726.3	726.3	727.3	728.3	729.2	730.2
170°	731.5	731.3	731.3	731.3	731.3	731.3	731.3	732.3	733.3	734.2	735.2
172.5°	734.3	734.0	734.1	734.2	734.3	734.5	734.6	735.6	736.6	737.5	738.5
175°	737.1	736.8	736.9	737.0	737.1	737.2	737.3	738.2	739.0	739.9	740.8
177.5°	738.2	737.9	738.0	738.1	738.2	738.3	738.4	739.4	740.4	741.3	742.3
180°	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5

TEST NUMBER: P1010803

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2
2.5°	1436.0	1437.3	1433.4	1425.6	1424.3	1426.9	1434.7	1432.1	1425.6	1437.3	1426.9
5°	1356.7	1350.1	1347.5	1350.1	1342.3	1338.4	1346.2	1342.3	1346.2	1347.5	1351.5
7.5°	1279.9	1281.2	1273.4	1274.7	1264.3	1266.9	1266.9	1266.9	1270.8	1273.4	1278.6
10°	1213.6	1216.2	1207.1	1208.4	1200.6	1195.4	1199.3	1207.1	1207.1	1207.1	1209.7
12.5°	1160.2	1148.5	1142.0	1140.7	1131.6	1129.0	1136.8	1139.4	1145.9	1145.9	1149.8
15°	1093.9	1091.3	1086.1	1086.1	1064.0	1069.2	1071.8	1080.9	1093.9	1083.5	1086.1
17.5°	1034.1	1027.6	1021.1	1018.5	1015.9	1008.1	1018.5	1017.2	1025.0	1026.3	1030.2
20°	980.7	975.5	962.5	963.8	966.4	954.7	961.2	961.2	969.0	976.8	985.9
22.5°	928.7	923.5	917.0	919.6	911.8	909.2	909.2	915.7	924.8	931.3	930.0
25°	888.4	879.3	875.4	871.5	867.6	870.2	866.3	872.8	879.3	883.2	879.3
27.5°	842.9	839.0	831.2	827.3	820.8	823.4	826.0	831.2	835.1	835.1	839.0
30°	798.6	793.4	790.8	786.9	786.9	781.7	783.0	788.2	792.1	796.0	801.2
32.5°	755.7	751.8	747.9	747.9	745.3	744.0	742.7	750.5	750.5	758.3	758.3
35°	720.6	714.1	714.1	707.6	710.2	708.9	706.3	711.5	712.8	718.0	716.7
37.5°	681.6	681.6	679.0	672.5	667.3	668.6	675.1	675.1	679.0	677.7	681.6
40°	642.6	640.0	640.0	636.1	634.8	633.5	634.8	636.1	642.6	641.3	642.6
42.5°	603.5	604.8	598.3	598.3	598.3	594.4	595.7	597.0	599.6	602.2	606.1
45°	565.8	563.2	561.9	559.3	556.7	558.0	556.7	561.9	560.6	563.2	567.1
47.5°	525.5	521.6	520.3	515.1	515.1	517.7	516.4	520.3	521.6	525.5	522.9
50°	486.5	481.3	477.4	478.7	470.9	473.5	473.5	477.4	481.3	482.6	485.2
52.5°	440.9	439.6	438.3	431.8	430.5	429.2	430.5	431.8	437.0	440.9	442.2
55°	396.7	395.4	387.6	385.0	381.1	381.1	383.7	385.0	394.1	395.4	400.6
57.5°	356.4	352.5	343.4	342.1	342.1	342.1	338.2	343.4	346.0	352.5	352.5
60°	312.2	312.2	304.4	304.4	305.7	304.4	304.4	305.7	305.7	310.9	313.5
62.5°	277.1	275.8	275.8	273.2	271.9	273.2	271.9	271.9	273.2	277.1	281.0
65°	245.8	244.5	243.2	241.9	239.3	239.3	240.6	243.2	243.2	245.8	247.1
67.5°	215.9	215.9	213.3	213.3	212.0	210.7	212.0	210.7	215.9	215.9	217.2
70°	186.0	184.7	180.8	179.5	175.6	176.9	176.9	180.8	182.1	184.7	187.3
72.5°	149.6	149.6	147.0	144.4	145.7	143.1	143.1	144.4	144.4	148.3	149.6
75°	123.6	121.0	119.7	121.0	119.7	122.3	119.7	119.7	122.3	122.3	122.3
77.5°	101.5	101.5	100.2	100.2	101.5	100.2	101.5	101.5	101.5	100.2	101.5
80°	83.2	81.9	81.9	81.9	80.6	80.6	80.6	80.6	80.6	80.6	80.6
82.5°	62.4	62.4	61.1	62.4	62.4	61.1	62.4	61.1	61.1	62.4	62.4
85°	41.6	44.2	41.6	41.6	42.9	42.9	44.2	42.9	44.2	41.6	42.9
87.5°	22.1	23.4	23.4	22.1	22.1	23.4	23.4	23.4	24.7	22.1	23.4
90°	15.4	15.5	15.8	16.0	16.3	16.5	16.3	16.0	15.8	15.5	15.4
92.5°	18.1	18.2	18.3	18.4	18.6	18.7	18.6	18.4	18.3	18.2	18.1
95°	20.9	20.9	20.9	20.9	20.9	20.9	20.9	20.9	20.9	20.9	20.9
97.5°	22.0	22.1	22.2	22.3	22.4	22.5	22.4	22.3	22.2	22.1	22.0
100°	22.5	22.6	22.7	22.8	23.0	23.1	23.0	22.8	22.7	22.6	22.5
102.5°	22.5	22.6	22.9	23.1	23.4	23.6	23.4	23.1	22.9	22.6	22.5
105°	23.1	23.2	23.5	23.7	24.0	24.2	24.0	23.7	23.5	23.2	23.1
107.5°	129.1	121.1	105.1	89.1	73.1	57.1	73.1	89.1	105.1	121.1	129.1
110°	229.7	221.0	203.5	186.0	168.6	151.1	168.6	186.0	203.5	221.0	229.7

TEST NUMBER: P1010803

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	287.4	287.3	287.0	286.8	286.5	286.3	286.5	286.8	287.0	287.3	287.4
115°	320.9	321.1	321.6	322.1	322.6	323.1	322.6	322.1	321.6	321.1	320.9
117.5°	352.2	352.3	352.4	352.5	352.6	352.7	352.6	352.5	352.4	352.3	352.2
120°	383.5	383.5	383.5	383.5	383.5	383.5	383.5	383.5	383.5	383.5	383.5
122.5°	413.2	413.3	413.4	413.5	413.6	413.7	413.6	413.5	413.4	413.3	413.2
125°	440.6	440.7	441.0	441.2	441.5	441.7	441.5	441.2	441.0	440.7	440.6
127.5°	470.3	470.2	469.9	469.7	469.4	469.2	469.4	469.7	469.9	470.2	470.3
130°	496.7	496.6	496.3	496.1	495.8	495.6	495.8	496.1	496.3	496.6	496.7
132.5°	521.4	521.2	520.9	520.5	520.2	519.8	520.2	520.5	520.9	521.2	521.4
135°	546.1	545.9	545.6	545.2	544.9	544.5	544.9	545.2	545.6	545.9	546.1
137.5°	569.2	569.1	568.8	568.6	568.3	568.1	568.3	568.6	568.8	569.1	569.2
140°	590.1	590.0	589.7	589.5	589.2	589.0	589.2	589.5	589.7	590.0	590.1
142.5°	609.9	609.7	609.3	609.0	608.6	608.2	608.6	609.0	609.3	609.7	609.9
145°	628.0	628.0	628.0	628.0	628.0	628.0	628.0	628.0	628.0	628.0	628.0
147.5°	645.0	644.7	644.1	643.5	642.9	642.3	642.9	643.5	644.1	644.7	645.0
150°	660.4	660.2	659.9	659.5	659.2	658.8	659.2	659.5	659.9	660.2	660.4
152.5°	674.7	674.4	673.8	673.2	672.6	672.0	672.6	673.2	673.8	674.4	674.7
155°	687.3	686.9	686.2	685.5	684.7	684.0	684.7	685.5	686.2	686.9	687.3
157.5°	698.9	698.4	697.4	696.5	695.5	694.5	695.5	696.5	697.4	698.4	698.9
160°	708.2	707.8	706.9	706.1	705.2	704.4	705.2	706.1	706.9	707.8	708.2
162.5°	717.0	716.6	715.9	715.2	714.4	713.7	714.4	715.2	715.9	716.6	717.0
165°	724.7	724.3	723.4	722.6	721.7	720.9	721.7	722.6	723.4	724.3	724.7
167.5°	730.7	730.2	729.2	728.3	727.3	726.3	727.3	728.3	729.2	730.2	730.7
170°	735.7	735.2	734.2	733.3	732.3	731.3	732.3	733.3	734.2	735.2	735.7
172.5°	739.0	738.4	737.3	736.2	735.1	734.0	735.1	736.2	737.3	738.4	739.0
175°	741.2	740.7	739.7	738.8	737.8	736.8	737.8	738.8	739.7	740.7	741.2
177.5°	742.8	742.2	741.0	739.7	738.5	737.3	738.5	739.7	741.0	742.2	742.8
180°	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5

TEST NUMBER: P1010803

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2	1519.2
2.5°	1437.3	1442.5	1437.3	1426.9	1437.3	1443.8	1450.3	1460.7	1465.9	1465.9	1473.7
5°	1355.4	1365.8	1361.9	1359.3	1369.7	1376.2	1386.6	1399.6	1413.9	1423.0	1433.4
7.5°	1282.5	1289.0	1295.5	1295.5	1305.9	1320.2	1335.8	1351.5	1369.7	1382.7	1390.5
10°	1218.8	1224.0	1227.9	1233.1	1248.7	1264.3	1285.1	1304.6	1320.2	1334.5	1347.5
12.5°	1157.6	1165.4	1174.6	1178.5	1190.2	1209.7	1229.2	1252.6	1277.3	1291.6	1304.6
15°	1099.1	1103.0	1113.4	1125.1	1135.5	1156.3	1181.1	1205.8	1226.6	1248.7	1260.4
17.5°	1039.3	1040.6	1067.9	1061.4	1095.2	1114.7	1127.7	1151.1	1185.0	1203.2	1221.4
20°	980.7	993.8	1005.5	1012.0	1030.2	1052.3	1090.0	1108.2	1135.5	1152.4	1168.0
22.5°	935.2	954.7	954.7	970.3	979.4	1000.3	1027.6	1062.7	1092.6	1104.3	1126.4
25°	894.9	904.0	919.6	924.8	941.7	959.9	978.1	1015.9	1048.4	1064.0	1079.6
27.5°	842.9	854.6	875.4	875.4	897.5	917.0	939.1	963.8	996.4	1018.5	1035.4
30°	802.5	814.3	823.4	837.7	846.8	865.0	904.0	922.2	950.8	970.3	991.2
32.5°	764.8	773.9	781.7	797.3	807.7	828.6	849.4	881.9	906.6	924.8	946.9
35°	723.2	732.3	742.7	754.4	770.0	789.5	809.0	836.4	861.1	878.0	896.2
37.5°	684.2	690.7	706.3	714.1	727.1	745.3	770.0	798.6	820.8	833.8	852.0
40°	646.5	651.7	663.4	677.7	686.8	701.1	727.1	751.8	779.1	794.7	809.0
42.5°	606.1	612.6	623.0	637.4	651.7	667.3	681.6	710.2	734.9	747.9	763.5
45°	571.0	574.9	582.7	597.0	611.3	623.0	645.2	671.2	694.6	705.0	721.9
47.5°	529.4	533.3	545.0	551.5	567.1	582.7	604.8	630.9	651.7	662.1	677.7
50°	486.5	490.4	498.2	512.5	522.9	539.8	559.3	581.4	607.4	621.7	630.9
52.5°	444.8	452.7	459.2	470.9	483.9	500.8	519.0	539.8	561.9	576.2	586.6
55°	403.2	409.7	417.5	424.0	439.6	455.3	476.1	495.6	515.1	528.1	539.8
57.5°	356.4	365.5	373.3	386.3	398.0	411.0	434.4	450.0	473.5	482.6	493.0
60°	316.1	325.2	331.7	342.1	352.5	369.4	385.0	404.5	424.0	435.7	448.7
62.5°	282.3	286.2	290.1	300.5	310.9	326.5	342.1	361.6	382.4	388.9	399.3
65°	248.4	252.3	258.8	267.9	275.8	284.9	301.8	317.4	336.9	347.3	351.2
67.5°	219.8	223.7	225.0	231.5	238.0	248.4	257.5	273.2	291.4	297.9	305.7
70°	187.3	193.8	195.1	200.3	202.9	209.4	219.8	231.5	245.8	257.5	264.0
72.5°	149.6	158.7	161.3	169.1	173.0	179.5	187.3	196.4	205.5	210.7	215.9
75°	122.3	124.9	126.2	132.7	139.2	148.3	152.2	157.4	165.2	171.7	176.9
77.5°	101.5	102.8	104.1	104.1	105.4	110.6	118.4	124.9	130.1	132.7	136.6
80°	81.9	80.6	80.6	81.9	81.9	81.9	84.5	93.7	96.3	102.8	101.5
82.5°	63.7	61.1	62.4	61.1	61.1	61.1	61.1	62.4	62.4	66.3	68.9
85°	41.6	42.9	41.6	41.6	40.3	41.6	40.3	40.3	39.0	39.0	37.7
87.5°	22.1	23.4	22.1	22.1	20.8	22.1	20.8	20.8	19.5	19.5	16.9
90°	15.2	14.7	14.2	13.7	13.2	11.6	10.0	8.4	6.8	6.0	5.4
92.5°	17.7	16.8	16.0	15.1	14.3	13.2	12.1	11.0	9.9	9.3	9.7
95°	20.5	19.6	18.7	17.9	17.0	15.7	14.3	13.0	11.7	11.0	13.5
97.5°	21.5	20.5	19.6	18.6	17.6	23.8	30.0	36.3	42.5	45.6	47.3
100°	22.0	21.0	20.1	19.1	18.1	37.1	56.2	75.2	94.3	103.8	102.6
102.5°	24.5	28.6	32.6	36.7	40.7	61.9	83.2	104.4	125.7	136.3	135.5
105°	33.9	55.5	77.1	98.7	120.3	131.3	142.3	153.3	164.3	169.8	169.1
107.5°	138.5	157.3	176.1	194.9	213.7	211.9	210.1	208.2	206.4	205.5	204.9
110°	231.7	235.7	239.8	243.8	247.8	246.4	245.1	243.7	242.4	241.7	241.2

TEST NUMBER: P1010803

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	286.8	285.7	284.6	283.5	282.4	281.1	279.7	278.4	277.1	276.4	276.0
115°	320.3	319.1	317.8	316.6	315.4	314.3	313.2	312.1	311.0	310.4	310.0
117.5°	351.7	350.7	349.8	348.8	347.8	347.2	346.6	345.9	345.3	345.0	344.6
120°	383.0	382.0	381.1	380.1	379.1	378.7	378.4	378.0	377.7	377.5	376.9
122.5°	412.9	412.3	411.6	411.0	410.4	409.9	409.4	408.9	408.4	408.2	407.8
125°	440.5	440.2	440.0	439.7	439.5	439.0	438.5	438.0	437.5	437.3	436.8
127.5°	470.1	469.8	469.4	469.1	468.7	468.1	467.5	466.8	466.2	465.9	465.4
130°	496.5	496.0	495.5	495.0	494.5	494.0	493.5	493.0	492.5	492.3	491.8
132.5°	521.2	520.7	520.2	519.7	519.2	518.8	518.5	518.1	517.8	517.6	517.1
135°	545.9	545.6	545.2	544.9	544.5	544.0	543.5	543.0	542.5	542.3	541.9
137.5°	568.9	568.3	567.7	567.1	566.5	566.3	566.0	565.8	565.5	565.4	564.9
140°	589.9	589.4	588.9	588.4	587.9	587.5	587.1	586.8	586.4	586.2	585.8
142.5°	609.7	609.3	609.0	608.6	608.2	607.8	607.5	607.1	606.8	606.6	606.2
145°	627.9	627.6	627.4	627.1	626.9	626.7	626.4	626.2	625.9	625.8	625.4
147.5°	644.9	644.6	644.4	644.1	643.9	643.7	643.4	643.2	642.9	642.8	642.5
150°	660.3	660.0	659.8	659.5	659.3	659.1	658.8	658.6	658.3	658.2	658.0
152.5°	674.5	674.0	673.5	673.0	672.5	672.4	672.3	672.2	672.1	672.0	671.9
155°	687.0	686.4	685.8	685.2	684.6	684.5	684.3	684.2	684.1	684.0	684.1
157.5°	698.5	697.8	697.1	696.3	695.6	695.7	695.8	695.9	696.0	696.1	696.1
160°	707.8	707.1	706.4	705.6	704.9	705.0	705.2	705.3	705.4	705.5	705.6
162.5°	716.6	715.7	714.9	714.0	713.2	713.3	713.4	713.5	713.6	713.7	713.9
165°	724.2	723.2	722.3	721.3	720.3	720.4	720.6	720.7	720.8	720.9	721.1
167.5°	730.2	729.2	728.3	727.3	726.3	726.3	726.3	726.3	726.3	726.3	726.5
170°	735.2	734.2	733.3	732.3	731.3	731.3	731.3	731.3	731.3	731.3	731.5
172.5°	738.5	737.5	736.6	735.6	734.6	734.5	734.3	734.2	734.1	734.0	734.3
175°	740.8	739.9	739.0	738.2	737.3	737.2	737.1	737.0	736.9	736.8	737.1
177.5°	742.3	741.3	740.4	739.4	738.4	738.3	738.2	738.1	738.0	737.9	738.2
180°	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5

TEST NUMBER: P1010803

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1519.2	1519.2	1519.2	1519.2
2.5°	1480.2	1489.3	1507.5	1523.1
5°	1449.0	1463.3	1490.6	1517.9
7.5°	1411.3	1433.4	1468.5	1506.2
10°	1374.9	1403.5	1446.4	1490.6
12.5°	1338.4	1368.4	1413.9	1471.1
15°	1295.5	1326.7	1381.4	1450.3
17.5°	1257.8	1299.4	1348.8	1417.8
20°	1217.5	1248.7	1312.4	1385.3
22.5°	1166.7	1218.8	1278.6	1355.4
25°	1126.4	1172.0	1231.8	1318.9
27.5°	1077.0	1130.3	1203.2	1279.9
30°	1036.7	1080.9	1148.5	1240.9
32.5°	989.8	1041.9	1112.1	1203.2
35°	948.2	992.5	1058.8	1151.1
37.5°	898.8	946.9	1021.1	1103.0
40°	855.9	902.7	972.9	1049.7
42.5°	803.8	853.3	923.5	988.5
45°	762.2	807.7	863.7	923.5
47.5°	711.5	759.6	814.3	855.9
50°	666.0	710.2	753.1	788.2
52.5°	616.5	656.9	695.9	721.9
55°	571.0	602.2	633.5	651.7
57.5°	517.7	547.6	573.6	584.0
60°	470.9	495.6	512.5	524.2
62.5°	421.4	439.6	452.7	459.2
65°	373.3	386.3	392.8	399.3
67.5°	323.9	335.6	339.5	347.3
70°	271.9	284.9	287.5	291.4
72.5°	232.8	232.8	238.0	243.2
75°	186.0	188.6	191.2	191.2
77.5°	145.7	145.7	148.3	149.6
80°	106.7	108.0	108.0	106.7
82.5°	72.8	75.4	72.8	71.5
85°	40.3	45.5	42.9	42.9
87.5°	16.9	16.9	19.5	16.9
90°	4.2	2.9	1.7	0.5
92.5°	10.4	11.1	11.9	12.6
95°	18.5	23.5	28.5	33.5
97.5°	50.7	54.2	57.6	61.0
100°	100.2	97.7	95.3	92.9
102.5°	133.9	132.3	130.7	129.1
105°	167.8	166.4	165.1	163.7
107.5°	203.8	202.7	201.6	200.5
110°	240.3	239.3	238.4	237.4

TEST NUMBER: P1010803

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	275.1	274.2	273.4	272.5
115°	309.3	308.6	307.8	307.1
117.5°	343.7	342.9	342.0	341.2
120°	375.8	374.7	373.6	372.5
122.5°	406.9	406.1	405.2	404.4
125°	435.8	434.9	433.9	432.9
127.5°	464.4	463.5	462.5	461.5
130°	490.8	489.9	488.9	487.9
132.5°	516.1	515.2	514.2	513.2
135°	541.2	540.5	539.7	539.0
137.5°	563.9	563.0	562.0	561.0
140°	585.1	584.4	583.6	582.9
142.5°	605.5	604.8	604.0	603.3
145°	624.5	623.7	622.8	622.0
147.5°	641.9	641.3	640.7	640.1
150°	657.7	657.3	657.0	656.6
152.5°	671.8	671.7	671.5	671.4
155°	684.4	684.6	684.9	685.1
157.5°	696.1	696.1	696.1	696.1
160°	705.7	705.8	705.9	706.0
162.5°	714.3	714.6	715.0	715.4
165°	721.4	721.8	722.1	722.5
167.5°	727.0	727.5	728.0	728.5
170°	732.0	732.5	733.0	733.5
172.5°	734.9	735.6	736.2	736.8
175°	737.7	738.3	738.9	739.5
177.5°	738.8	739.4	740.0	740.6
180°	739.5	739.5	739.5	739.5

(END OF REPORT)