

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010849

Luminaire Tested: S123RDIP-B1165D585UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010849
REPORT IS A COMBINATION OF REPORTS P993045 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1165D585UB2750-4F0-XX-W2A-A_2700K
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6869.0 lumens
Efficiency: N/A
Efficacy: 89.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010849

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1010849

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71			66
1	102	98	94	91	96	93	89	86	82	80	78	73	71	69	64	63	61			57
2	94	87	81	76	88	82	77	72	73	69	66	65	62	59	57	55	53			49
3	86	77	70	64	81	73	66	61	65	60	56	58	54	51	51	49	46			43
4	79	69	61	55	74	65	58	53	58	53	48	52	48	44	46	43	40			37
5	73	62	54	48	69	58	51	46	53	47	42	47	43	39	42	39	36			33
6	67	56	48	42	64	53	46	40	48	42	37	43	38	35	39	35	32			29
7	63	50	43	37	59	48	41	36	44	38	33	39	34	31	35	31	28			26
8	58	46	38	33	55	44	37	32	40	34	30	36	31	28	33	29	26			24
9	54	42	35	30	51	40	34	29	37	31	27	33	29	25	30	26	23			21
10	51	39	32	27	48	37	31	26	34	28	25	31	26	23	28	24	21			19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19634	19634	19634	19634
5°	19649	22613	19700	16777
10°	19476	27297	19560	14653
15°	19275	30981	19275	12920
20°	18880	33417	18986	11462
25°	18591	31749	18554	10458
30°	18255	21998	18215	9477
35°	17849	14124	17769	8737
40°	17345	9972	17258	8001
45°	16467	7981	16443	7285
50°	15390	6677	15339	6447
55°	14177	5502	14064	5465
60°	12987	4548	12857	4647
65°	11589	3640	11666	3940
70°	10301	2529	10578	3185
75°	8734	1875	9088	2449
80°	6955	1244	7546	1836
85°	4947	587	5398	1141

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 26212 cd/sqm

TEST NUMBER: P1010849

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.1	2.6
10°-20°	560.7	8.2
20°-30°	883.2	12.9
30°-40°	918.3	13.4
40°-50°	785.7	11.4
50°-60°	599.0	8.7
60°-70°	383.8	5.6
70°-80°	183.9	2.7
80°-90°	49.9	0.7
90°-100°	26.9	0.4
100°-110°	130.0	1.9
110°-120°	318.7	4.6
120°-130°	404.6	5.9
130°-140°	432.2	6.3
140°-150°	404.2	5.9
150°-160°	326.0	4.7
160°-170°	210.4	3.1
170°-180°	72.5	1.1
0°-30°	1623.0	23.6
0°-40°	2541.4	37.0
0°-60°	3926.0	57.2
0°-90°	4543.5	66.1
90°-120°	475.6	6.9
90°-150°	1716.6	25.0
90°-180°	2325.0	33.8
0°-180°	6869.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1824	1824	1824	1824	1824	
5°	1822	2166	1827	1607	1822	173
15°	1741	3078	1741	1284	1741	490
25°	1584	3172	1580	1045	1584	729
35°	1382	1376	1376	851	1382	865
45°	1109	734	1107	670	1109	854
55°	782	461	776	458	782	701
65°	479	266	483	287	479	479
75°	230	112	239	147	230	248
85°	52	26	56	52	52	58
90°	1	17	1	17	1	5
95°	35	22	35	22	35	41
105°	169	25	169	25	169	179
115°	317	333	317	333	317	313
125°	447	456	447	456	447	399
135°	556	562	556	562	556	428
145°	642	648	642	648	642	402
155°	707	706	707	706	707	326
165°	745	744	745	744	745	211
175°	763	760	763	760	763	73
180°	763	763	763	763	763	

TEST NUMBER: P1010849

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1
2.5°	1828.7	1841.2	1850.6	1856.9	1872.5	1881.8	1889.6	1903.7	1903.7	1906.8	1913.1
5°	1822.5	1849.0	1867.8	1892.8	1925.6	1941.2	1963.0	1981.8	2008.3	2022.4	2036.4
7.5°	1808.4	1845.9	1885.0	1922.4	1970.9	2002.1	2024.0	2072.4	2106.7	2148.9	2181.7
10°	1789.7	1841.2	1891.2	1949.0	2014.6	2061.4	2094.2	2158.3	2223.8	2283.2	2333.2
12.5°	1766.3	1828.7	1900.6	1970.9	2063.0	2109.8	2162.9	2242.6	2336.3	2411.3	2478.4
15°	1741.3	1813.1	1894.3	1980.2	2095.8	2161.4	2237.9	2334.7	2439.4	2547.1	2639.3
17.5°	1702.2	1792.8	1883.4	2008.3	2144.2	2183.2	2248.8	2381.6	2511.2	2608.0	2720.5
20°	1663.2	1764.7	1878.7	1991.2	2138.0	2228.5	2289.4	2430.0	2569.0	2686.1	2793.9
22.5°	1627.3	1733.5	1852.2	1994.3	2131.7	2222.3	2298.8	2445.6	2606.5	2737.6	2870.4
25°	1583.6	1699.1	1830.3	1964.6	2131.7	2200.4	2284.8	2455.0	2625.2	2776.7	2940.7
27.5°	1536.7	1653.8	1783.5	1920.9	2073.9	2175.4	2258.2	2440.9	2648.6	2811.0	2979.7
30°	1489.9	1610.1	1735.0	1858.4	2030.2	2127.0	2222.3	2423.7	2661.1	2847.0	2976.6
32.5°	1444.6	1546.1	1669.4	1789.7	1959.9	2066.1	2173.9	2406.6	2665.8	2822.0	2884.4
35°	1382.1	1488.3	1588.2	1716.3	1888.1	1992.7	2119.2	2405.0	2645.5	2742.3	2711.1
37.5°	1324.3	1413.3	1508.6	1622.6	1799.1	1934.9	2066.1	2364.4	2578.4	2584.6	2408.1
40°	1260.3	1333.7	1413.3	1533.6	1724.1	1858.4	2000.5	2301.9	2456.5	2364.4	2053.6
42.5°	1186.9	1252.5	1314.9	1432.1	1639.8	1789.7	1942.7	2223.8	2280.1	2067.7	1744.4
45°	1108.8	1161.9	1219.7	1343.1	1550.8	1699.1	1852.2	2103.6	2045.8	1746.0	1438.3
47.5°	1027.6	1072.9	1129.1	1241.5	1455.5	1607.0	1752.2	1931.8	1785.0	1463.3	1205.6
50°	946.4	982.3	1037.0	1152.5	1358.7	1496.1	1630.4	1747.5	1541.4	1255.6	996.4
52.5°	866.7	894.8	951.1	1049.5	1249.4	1380.5	1477.4	1522.6	1313.4	1037.0	865.2
55°	782.4	813.6	851.1	951.1	1149.4	1246.2	1310.3	1308.7	1093.2	879.2	715.3
57.5°	701.2	729.3	762.1	862.1	1022.9	1088.5	1143.2	1116.6	912.0	719.9	613.7
60°	629.4	645.0	680.9	765.2	887.0	943.3	974.5	929.2	744.9	607.5	507.5
62.5°	551.3	566.9	596.6	676.2	751.2	780.8	807.4	749.6	615.3	495.1	434.2
65°	479.4	499.7	518.5	582.5	623.1	659.0	655.9	607.5	481.0	402.9	352.9
67.5°	417.0	424.8	440.4	479.4	498.2	524.7	526.3	471.6	387.3	328.0	298.3
70°	349.8	357.6	368.6	387.3	399.8	406.0	402.9	354.5	292.0	256.1	229.6
72.5°	292.0	290.5	298.3	298.3	310.8	309.2	299.8	262.4	221.8	192.1	176.5
75°	229.6	231.1	232.7	229.6	224.9	218.6	210.8	182.7	156.2	142.1	128.1
77.5°	179.6	176.5	178.0	167.1	160.9	154.6	143.7	129.6	107.8	104.6	98.4
80°	128.1	126.5	124.9	120.3	106.2	99.9	92.1	84.3	79.6	76.5	75.0
82.5°	85.9	85.9	82.8	73.4	65.6	60.9	59.3	56.2	51.5	51.5	50.0
85°	51.5	50.0	46.9	37.5	32.8	32.8	32.8	32.8	29.7	29.7	28.1
87.5°	20.3	18.7	14.1	14.1	12.5	12.5	12.5	10.9	10.9	9.4	9.4
90°	0.6	1.8	3.1	4.3	5.6	6.2	7.0	8.7	10.3	12.0	13.6
92.5°	13.0	12.2	11.5	10.7	10.0	9.6	10.2	11.3	12.4	13.6	14.7
95°	34.6	29.4	24.2	19.1	13.9	11.3	12.0	13.4	14.8	16.2	17.6
97.5°	62.9	59.4	55.8	52.3	48.8	47.0	43.8	37.4	30.9	24.5	18.1
100°	95.8	98.3	100.8	103.3	105.8	107.1	97.3	77.6	58.0	38.3	18.7
102.5°	133.2	134.8	136.4	138.1	139.7	140.5	129.5	107.6	85.7	63.8	41.9
105°	168.9	170.3	171.7	173.0	174.4	175.1	169.4	158.1	146.8	135.4	124.1
107.5°	206.9	208.0	209.2	210.3	211.4	212.0	212.9	214.8	216.7	218.6	220.5
110°	244.8	245.8	246.8	247.9	248.9	249.4	250.1	251.5	252.8	254.2	255.6



TEST NUMBER: P1010849

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	281.1	282.0	282.9	283.8	284.7	285.1	285.8	287.2	288.5	289.9	291.3
115°	316.8	317.6	318.3	319.1	319.8	320.2	320.8	321.9	323.0	324.2	325.3
117.5°	351.9	352.8	353.7	354.6	355.5	355.9	356.2	356.8	357.5	358.1	358.7
120°	384.2	385.3	386.5	387.6	388.7	389.3	389.5	389.9	390.2	390.6	391.0
122.5°	417.1	418.0	418.9	419.8	420.7	421.1	421.3	421.8	422.3	422.8	423.3
125°	446.6	447.6	448.6	449.6	450.6	451.1	451.4	451.9	452.4	452.9	453.4
127.5°	476.0	477.0	478.0	479.1	480.1	480.6	480.9	481.5	482.2	482.8	483.4
130°	503.2	504.2	505.2	506.3	507.3	507.8	508.0	508.5	509.0	509.5	510.0
132.5°	529.3	530.3	531.3	532.4	533.4	533.9	534.1	534.5	534.8	535.2	535.6
135°	556.0	556.8	557.5	558.3	559.0	559.4	559.6	560.1	560.6	561.1	561.6
137.5°	578.6	579.6	580.6	581.7	582.7	583.2	583.3	583.6	583.8	584.1	584.3
140°	601.3	602.1	602.8	603.6	604.3	604.7	604.9	605.3	605.6	606.0	606.4
142.5°	622.3	623.1	623.8	624.6	625.3	625.7	625.9	626.3	626.6	627.0	627.4
145°	641.5	642.4	643.3	644.2	645.1	645.5	645.6	645.9	646.1	646.4	646.6
147.5°	660.2	660.8	661.5	662.1	662.8	663.1	663.2	663.5	663.7	664.0	664.2
150°	677.2	677.6	678.0	678.3	678.7	678.9	679.0	679.3	679.6	679.8	680.1
152.5°	692.5	692.6	692.8	692.9	693.0	693.1	693.2	693.3	693.4	693.6	693.7
155°	706.7	706.5	706.2	706.0	705.7	705.6	705.7	705.8	705.9	706.0	706.1
157.5°	718.0	718.0	718.0	718.0	718.0	718.0	717.9	717.8	717.7	717.6	717.5
160°	728.2	728.1	728.0	727.9	727.8	727.7	727.6	727.5	727.4	727.2	727.1
162.5°	737.9	737.5	737.1	736.8	736.4	736.2	736.1	736.0	735.9	735.7	735.6
165°	745.2	744.8	744.4	744.1	743.7	743.5	743.4	743.3	743.2	743.1	743.0
167.5°	751.5	751.0	750.5	750.0	749.5	749.2	749.2	749.2	749.2	749.2	749.2
170°	756.6	756.1	755.6	755.1	754.6	754.3	754.3	754.3	754.3	754.3	754.3
172.5°	760.0	759.4	758.7	758.1	757.4	757.1	757.2	757.3	757.4	757.6	757.7
175°	762.8	762.2	761.6	760.9	760.3	760.0	760.1	760.2	760.3	760.4	760.5
177.5°	763.9	763.3	762.7	762.0	761.4	761.1	761.2	761.3	761.4	761.6	761.7
180°	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8

TEST NUMBER: P1010849

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1
2.5°	1925.6	1925.6	1939.6	1953.7	1945.9	1950.6	1967.7	1961.5	1974.0	1972.4	1977.1
5°	2070.8	2088.0	2102.0	2131.7	2136.4	2131.7	2161.4	2169.2	2183.2	2166.1	2173.9
7.5°	2234.8	2270.7	2305.1	2348.8	2362.8	2366.0	2381.6	2403.4	2422.2	2387.8	2405.0
10°	2394.1	2448.7	2519.0	2558.1	2592.4	2604.9	2617.4	2631.5	2653.3	2673.6	2658.0
12.5°	2565.9	2645.5	2712.7	2782.9	2825.1	2820.4	2856.3	2865.7	2882.9	2887.6	2893.8
15°	2706.4	2818.9	2861.0	2965.7	2975.0	3006.3	3046.9	3082.8	3087.5	3078.1	3078.1
17.5°	2840.7	2937.5	3012.5	3096.8	3114.0	3140.6	3192.1	3209.3	3215.5	3214.0	3214.0
20°	2950.0	3014.1	3140.6	3210.8	3238.9	3273.3	3309.2	3331.1	3335.8	3342.0	3332.7
22.5°	3021.9	3118.7	3221.8	3279.6	3303.0	3315.5	3338.9	3345.1	3337.3	3338.9	3340.5
25°	3078.1	3173.4	3235.8	3251.4	3249.9	3234.3	3217.1	3187.4	3184.3	3171.8	3146.8
27.5°	3093.7	3129.6	3121.8	3057.8	2993.8	2987.5	2884.4	2828.2	2764.2	2773.6	2737.6
30°	3009.4	2962.5	2851.6	2689.2	2622.1	2512.8	2397.2	2276.9	2230.1	2178.6	2273.8
32.5°	2803.2	2636.1	2439.4	2228.5	2116.1	2019.3	1895.9	1808.4	1758.5	1716.3	1797.5
35°	2492.5	2231.7	1970.9	1771.0	1678.8	1591.4	1475.8	1432.1	1369.6	1375.9	1383.7
37.5°	2092.7	1805.3	1608.5	1411.8	1350.9	1314.9	1230.6	1163.5	1141.6	1135.3	1135.3
40°	1717.9	1482.0	1307.1	1152.5	1105.7	1076.0	1008.9	977.6	954.2	947.9	955.8
42.5°	1421.1	1219.7	1083.8	980.7	947.9	910.5	882.4	843.3	838.6	827.7	841.8
45°	1193.1	1018.2	916.7	841.8	813.6	799.6	768.4	744.9	735.6	734.0	744.9
47.5°	1012.0	876.1	787.1	740.2	718.4	704.3	677.8	668.4	659.0	662.2	657.5
50°	849.6	748.1	690.3	648.1	634.0	620.0	602.8	593.4	588.8	588.8	587.2
52.5°	729.3	645.0	607.5	568.5	562.2	554.4	535.7	529.4	521.6	520.0	526.3
55°	624.7	566.9	529.4	506.0	499.7	484.1	476.3	468.5	463.8	460.7	462.3
57.5°	534.1	490.4	465.4	445.1	434.2	427.9	413.8	412.3	409.2	409.2	407.6
60°	459.1	427.9	398.2	385.7	377.9	370.1	368.6	359.2	354.5	357.6	356.1
62.5°	388.9	363.9	346.7	332.6	328.0	321.7	317.0	313.9	309.2	310.8	310.8
65°	324.8	304.5	292.0	279.5	278.0	271.7	270.2	267.0	267.0	265.5	268.6
67.5°	267.0	253.0	242.1	234.3	229.6	231.1	224.9	220.2	220.2	218.6	223.3
70°	212.4	204.6	193.6	184.3	178.0	178.0	170.2	168.7	168.7	168.7	167.1
72.5°	164.0	149.9	145.2	142.1	142.1	142.1	139.0	139.0	137.4	139.0	137.4
75°	121.8	120.3	117.1	115.6	115.6	114.0	112.4	112.4	112.4	112.4	112.4
77.5°	95.3	95.3	92.1	90.6	90.6	90.6	89.0	89.0	87.5	87.5	87.5
80°	70.3	70.3	67.2	67.2	67.2	65.6	65.6	65.6	67.2	65.6	65.6
82.5°	48.4	48.4	46.9	48.4	46.9	45.3	45.3	45.3	43.7	45.3	45.3
85°	28.1	28.1	26.5	25.0	26.5	26.5	25.0	26.5	25.0	26.5	25.0
87.5°	10.9	9.4	9.4	9.4	7.8	9.4	7.8	7.8	9.4	7.8	9.4
90°	14.1	14.6	15.1	15.6	15.9	16.0	16.3	16.5	16.8	17.0	16.8
92.5°	15.6	16.5	17.4	18.3	18.7	18.8	18.9	19.0	19.2	19.3	19.2
95°	18.5	19.3	20.2	21.1	21.5	21.5	21.5	21.5	21.5	21.5	21.5
97.5°	19.1	20.1	21.2	22.2	22.7	22.8	22.9	23.0	23.1	23.2	23.1
100°	19.7	20.7	21.7	22.7	23.2	23.3	23.4	23.5	23.7	23.8	23.7
102.5°	37.7	33.6	29.4	25.3	23.2	23.3	23.6	23.9	24.1	24.4	24.1
105°	101.8	79.5	57.2	34.9	23.8	23.9	24.2	24.4	24.7	24.9	24.7
107.5°	201.1	181.7	162.3	142.9	133.2	124.9	108.4	91.9	75.4	58.9	75.4
110°	251.4	247.3	243.1	239.0	236.9	227.9	209.9	191.8	173.8	155.8	173.8

TEST NUMBER: P1010849

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	292.4	293.6	294.7	295.8	296.4	296.3	296.0	295.8	295.5	295.3	295.5
115°	326.6	327.8	329.1	330.4	331.0	331.2	331.7	332.2	332.7	333.2	332.7
117.5°	359.7	360.7	361.8	362.8	363.3	363.4	363.5	363.6	363.7	363.8	363.7
120°	392.0	393.0	394.1	395.1	395.6	395.6	395.6	395.6	395.6	395.6	395.6
122.5°	423.9	424.6	425.2	425.9	426.2	426.3	426.4	426.5	426.6	426.7	426.6
125°	453.6	453.9	454.1	454.4	454.5	454.6	454.9	455.1	455.4	455.6	455.4
127.5°	483.8	484.2	484.5	484.9	485.1	485.0	484.7	484.5	484.2	484.0	484.2
130°	510.5	511.0	511.5	512.0	512.3	512.2	511.9	511.7	511.4	511.2	511.4
132.5°	536.1	536.6	537.1	537.6	537.8	537.6	537.2	536.9	536.5	536.1	536.5
135°	562.0	562.4	562.7	563.1	563.3	563.1	562.7	562.4	562.0	561.6	562.0
137.5°	584.9	585.5	586.2	586.8	587.1	587.0	586.7	586.5	586.2	586.0	586.2
140°	606.9	607.4	607.9	608.4	608.7	608.6	608.3	608.0	607.8	607.5	607.8
142.5°	627.8	628.2	628.5	628.9	629.1	628.9	628.5	628.2	627.8	627.4	627.8
145°	646.9	647.1	647.4	647.7	647.8	647.8	647.8	647.8	647.8	647.8	647.8
147.5°	664.4	664.7	664.9	665.2	665.3	665.0	664.4	663.7	663.1	662.5	663.1
150°	680.3	680.6	680.8	681.1	681.2	681.0	680.6	680.3	679.9	679.5	679.9
152.5°	694.2	694.7	695.2	695.7	695.9	695.6	695.0	694.3	693.7	693.1	693.7
155°	706.7	707.4	708.0	708.7	709.0	708.6	707.9	707.1	706.4	705.6	706.4
157.5°	718.3	719.0	719.8	720.5	720.9	720.4	719.4	718.3	717.3	716.3	717.3
160°	727.9	728.6	729.4	730.1	730.5	730.1	729.2	728.3	727.4	726.5	727.4
162.5°	736.5	737.4	738.3	739.2	739.6	739.2	738.5	737.7	737.0	736.2	737.0
165°	744.0	745.0	746.0	747.0	747.5	747.1	746.2	745.3	744.4	743.5	744.4
167.5°	750.2	751.2	752.2	753.2	753.7	753.2	752.2	751.2	750.2	749.2	750.2
170°	755.3	756.3	757.3	758.3	758.8	758.3	757.3	756.3	755.3	754.3	755.3
172.5°	758.7	759.7	760.7	761.7	762.2	761.6	760.5	759.4	758.2	757.1	758.2
175°	761.4	762.3	763.2	764.1	764.5	764.0	763.0	762.0	761.0	760.0	761.0
177.5°	762.7	763.7	764.7	765.7	766.2	765.6	764.3	763.0	761.8	760.5	761.8
180°	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8

TEST NUMBER: P1010849

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1
2.5°	1969.3	1959.9	1953.7	1949.0	1944.3	1958.4	1939.6	1919.3	1905.3	1895.9	1892.8
5°	2175.4	2155.1	2138.0	2123.9	2127.0	2127.0	2094.2	2058.3	2027.1	2009.9	1991.2
7.5°	2414.4	2392.5	2358.2	2350.3	2344.1	2305.1	2272.3	2206.7	2167.6	2128.6	2094.2
10°	2651.8	2623.6	2590.8	2579.9	2564.3	2515.9	2465.9	2381.6	2333.2	2261.3	2216.0
12.5°	2873.5	2839.2	2806.4	2798.6	2775.1	2733.0	2647.1	2559.6	2476.8	2400.3	2320.7
15°	3059.4	3050.0	3000.0	2968.8	2917.2	2859.5	2840.7	2722.0	2617.4	2537.7	2394.1
17.5°	3215.5	3171.8	3124.9	3104.6	3084.3	3017.2	2950.0	2828.2	2715.8	2598.7	2506.5
20°	3340.5	3292.0	3259.3	3229.6	3220.2	3143.7	3037.5	2929.7	2806.4	2675.2	2554.9
22.5°	3346.7	3340.5	3318.6	3301.4	3282.7	3232.7	3148.4	3014.1	2882.9	2739.2	2581.5
25°	3217.1	3207.7	3270.2	3254.6	3267.1	3248.3	3203.0	3090.6	2937.5	2768.9	2609.6
27.5°	2826.7	2921.9	3020.3	3054.7	3078.1	3145.2	3167.1	3104.6	2981.3	2801.7	2623.6
30°	2295.7	2422.2	2581.5	2667.4	2733.0	2857.9	3020.3	3040.6	2982.8	2839.2	2620.5
32.5°	1802.2	1917.8	2045.8	2147.3	2234.8	2490.9	2709.5	2867.3	2895.4	2820.4	2628.3
35°	1452.4	1502.3	1624.2	1721.0	1839.7	2058.3	2316.0	2570.5	2742.3	2751.7	2604.9
37.5°	1197.8	1224.4	1330.6	1385.2	1455.5	1647.6	1888.1	2220.7	2487.8	2614.3	2539.3
40°	991.7	1052.6	1113.5	1144.7	1194.7	1327.4	1558.6	1819.4	2150.4	2384.7	2437.8
42.5°	860.5	887.0	926.1	969.8	1001.0	1116.6	1271.2	1510.2	1808.4	2134.8	2281.6
45°	759.0	768.4	809.0	837.1	869.9	951.1	1060.4	1260.3	1522.6	1844.4	2094.2
47.5°	674.7	693.4	715.3	732.4	754.3	816.8	910.5	1055.7	1286.8	1574.2	1842.8
50°	599.7	610.6	638.7	646.5	662.2	705.9	777.7	888.6	1079.1	1308.7	1586.7
52.5°	529.4	549.7	560.6	571.6	585.6	621.6	668.4	759.0	902.7	1118.2	1354.0
55°	474.8	481.0	496.6	506.0	516.9	541.9	582.5	649.7	762.1	933.9	1157.2
57.5°	421.7	421.7	437.3	445.1	456.0	474.8	510.7	562.2	643.4	771.5	976.1
60°	365.4	367.0	379.5	388.9	392.0	410.7	440.4	481.0	543.5	637.2	804.3
62.5°	315.5	323.3	329.5	332.6	343.6	354.5	379.5	407.6	451.3	534.1	652.8
65°	273.3	274.9	279.5	282.7	287.4	299.8	318.6	337.3	374.8	435.7	532.5
67.5°	224.9	231.1	237.4	237.4	242.1	248.3	267.0	282.7	310.8	346.7	412.3
70°	168.7	171.8	181.2	185.8	192.1	203.0	212.4	221.8	243.6	270.2	320.1
72.5°	140.6	140.6	143.7	145.2	145.2	153.0	167.1	176.5	187.4	206.1	240.5
75°	112.4	112.4	117.1	115.6	118.7	121.8	123.4	129.6	135.9	149.9	170.2
77.5°	89.0	90.6	90.6	92.1	92.1	93.7	95.3	98.4	101.5	109.3	118.7
80°	65.6	67.2	67.2	68.7	68.7	70.3	71.8	73.4	76.5	79.6	84.3
82.5°	45.3	46.9	46.9	48.4	46.9	48.4	50.0	50.0	51.5	54.7	56.2
85°	26.5	26.5	28.1	26.5	26.5	26.5	28.1	28.1	29.7	34.4	34.4
87.5°	7.8	9.4	7.8	9.4	9.4	9.4	9.4	10.9	10.9	12.5	14.1
90°	16.5	16.3	16.0	15.9	15.6	15.1	14.6	14.1	13.6	12.0	10.3
92.5°	19.0	18.9	18.8	18.7	18.3	17.4	16.5	15.6	14.7	13.6	12.4
95°	21.5	21.5	21.5	21.5	21.1	20.2	19.3	18.5	17.6	16.2	14.8
97.5°	23.0	22.9	22.8	22.7	22.2	21.2	20.1	19.1	18.1	24.5	30.9
100°	23.5	23.4	23.3	23.2	22.7	21.7	20.7	19.7	18.7	38.3	58.0
102.5°	23.9	23.6	23.3	23.2	25.3	29.4	33.6	37.7	41.9	63.8	85.7
105°	24.4	24.2	23.9	23.8	34.9	57.2	79.5	101.8	124.1	135.4	146.8
107.5°	91.9	108.4	124.9	133.2	142.9	162.3	181.7	201.1	220.5	218.6	216.7
110°	191.8	209.9	227.9	236.9	239.0	243.1	247.3	251.4	255.6	254.2	252.8

TEST NUMBER: P1010849

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	295.8	296.0	296.3	296.4	295.8	294.7	293.6	292.4	291.3	289.9	288.5
115°	332.2	331.7	331.2	331.0	330.4	329.1	327.8	326.6	325.3	324.2	323.0
117.5°	363.6	363.5	363.4	363.3	362.8	361.8	360.7	359.7	358.7	358.1	357.5
120°	395.6	395.6	395.6	395.6	395.1	394.1	393.0	392.0	391.0	390.6	390.2
122.5°	426.5	426.4	426.3	426.2	425.9	425.2	424.6	423.9	423.3	422.8	422.3
125°	455.1	454.9	454.6	454.5	454.4	454.1	453.9	453.6	453.4	452.9	452.4
127.5°	484.5	484.7	485.0	485.1	484.9	484.5	484.2	483.8	483.4	482.8	482.2
130°	511.7	511.9	512.2	512.3	512.0	511.5	511.0	510.5	510.0	509.5	509.0
132.5°	536.9	537.2	537.6	537.8	537.6	537.1	536.6	536.1	535.6	535.2	534.8
135°	562.4	562.7	563.1	563.3	563.1	562.7	562.4	562.0	561.6	561.1	560.6
137.5°	586.5	586.7	587.0	587.1	586.8	586.2	585.5	584.9	584.3	584.1	583.8
140°	608.0	608.3	608.6	608.7	608.4	607.9	607.4	606.9	606.4	606.0	605.6
142.5°	628.2	628.5	628.9	629.1	628.9	628.5	628.2	627.8	627.4	627.0	626.6
145°	647.8	647.8	647.8	647.8	647.7	647.4	647.1	646.9	646.6	646.4	646.1
147.5°	663.7	664.4	665.0	665.3	665.2	664.9	664.7	664.4	664.2	664.0	663.7
150°	680.3	680.6	681.0	681.2	681.1	680.8	680.6	680.3	680.1	679.8	679.6
152.5°	694.3	695.0	695.6	695.9	695.7	695.2	694.7	694.2	693.7	693.6	693.4
155°	707.1	707.9	708.6	709.0	708.7	708.0	707.4	706.7	706.1	706.0	705.9
157.5°	718.3	719.4	720.4	720.9	720.5	719.8	719.0	718.3	717.5	717.6	717.7
160°	728.3	729.2	730.1	730.5	730.1	729.4	728.6	727.9	727.1	727.2	727.4
162.5°	737.7	738.5	739.2	739.6	739.2	738.3	737.4	736.5	735.6	735.7	735.9
165°	745.3	746.2	747.1	747.5	747.0	746.0	745.0	744.0	743.0	743.1	743.2
167.5°	751.2	752.2	753.2	753.7	753.2	752.2	751.2	750.2	749.2	749.2	749.2
170°	756.3	757.3	758.3	758.8	758.3	757.3	756.3	755.3	754.3	754.3	754.3
172.5°	759.4	760.5	761.6	762.2	761.7	760.7	759.7	758.7	757.7	757.6	757.4
175°	762.0	763.0	764.0	764.5	764.1	763.2	762.3	761.4	760.5	760.4	760.3
177.5°	763.0	764.3	765.6	766.2	765.7	764.7	763.7	762.7	761.7	761.6	761.4
180°	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8

TEST NUMBER: P1010849

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1
2.5°	1888.1	1880.3	1872.5	1872.5	1855.3	1839.7	1831.9	1835.0	1825.6	1813.1	1800.6
5°	1970.9	1939.6	1933.4	1916.2	1892.8	1860.0	1842.8	1827.2	1808.4	1783.5	1760.0
7.5°	2047.4	2006.8	1984.9	1967.7	1922.4	1877.2	1839.7	1814.7	1781.9	1744.4	1716.3
10°	2147.3	2072.4	2048.9	2009.9	1945.9	1881.8	1838.1	1797.5	1752.2	1708.5	1671.0
12.5°	2227.0	2141.1	2097.4	2058.3	1975.5	1894.3	1820.9	1771.0	1716.3	1667.9	1619.5
15°	2317.6	2220.7	2144.2	2097.4	1992.7	1894.3	1811.6	1741.3	1680.4	1621.0	1578.9
17.5°	2361.3	2239.5	2205.1	2138.0	1986.5	1888.1	1786.6	1711.6	1638.2	1569.5	1519.5
20°	2430.0	2287.9	2202.0	2156.7	2022.4	1877.2	1758.5	1672.6	1596.0	1522.6	1469.6
22.5°	2434.7	2280.1	2223.8	2138.0	1972.4	1844.4	1733.5	1628.8	1539.8	1471.1	1416.5
25°	2423.7	2266.0	2187.9	2119.2	1981.8	1825.6	1683.5	1580.4	1493.0	1413.3	1349.3
27.5°	2419.1	2225.4	2152.0	2083.3	1928.7	1771.0	1653.8	1536.7	1436.8	1366.5	1300.9
30°	2412.8	2181.7	2092.7	2013.0	1870.9	1728.8	1588.2	1486.7	1391.5	1302.5	1236.9
32.5°	2372.2	2122.3	2031.8	1947.4	1794.4	1652.3	1541.4	1433.6	1330.6	1247.8	1188.4
35°	2359.7	2067.7	1949.0	1858.4	1708.5	1582.0	1464.9	1375.9	1279.0	1196.3	1126.0
37.5°	2323.8	2011.5	1883.4	1767.8	1611.7	1491.4	1405.5	1316.5	1222.8	1133.8	1077.6
40°	2261.3	1945.9	1800.6	1681.9	1521.1	1399.3	1319.6	1254.0	1161.9	1082.3	1013.5
42.5°	2169.2	1878.7	1722.5	1597.6	1419.6	1305.6	1240.0	1177.5	1099.4	1016.7	960.4
45°	2063.0	1789.7	1644.5	1505.5	1324.3	1213.4	1144.7	1107.2	1035.4	965.1	899.5
47.5°	1917.8	1697.6	1553.9	1410.2	1225.9	1118.2	1063.5	1026.0	976.1	899.5	846.4
50°	1735.0	1578.9	1443.0	1314.9	1129.1	1026.0	971.4	943.3	901.1	846.4	794.9
52.5°	1532.0	1441.4	1329.0	1210.3	1030.7	933.9	883.9	862.1	830.8	779.3	735.6
55°	1327.4	1288.4	1211.9	1094.7	927.6	848.0	804.3	776.2	752.7	715.3	677.8
57.5°	1144.7	1126.0	1072.9	982.3	841.8	759.0	721.5	702.8	684.0	655.9	618.4
60°	955.8	976.1	921.4	876.1	748.1	676.2	643.4	623.1	613.7	588.8	565.3
62.5°	791.8	810.5	779.3	744.9	654.3	590.3	570.0	551.3	545.0	523.2	499.7
65°	643.4	666.8	643.4	624.7	570.0	516.9	491.9	482.6	476.3	462.3	443.5
67.5°	512.2	535.7	524.7	501.3	484.1	440.4	426.3	417.0	413.8	402.9	387.3
70°	385.7	418.5	421.7	407.6	392.0	371.7	362.3	359.2	351.4	342.0	332.6
72.5°	278.0	315.5	317.0	317.0	307.7	307.7	298.3	293.6	293.6	284.2	273.3
75°	204.6	229.6	232.7	235.8	240.5	245.2	238.9	238.9	237.4	228.0	223.3
77.5°	135.9	157.7	165.5	176.5	182.7	182.7	185.8	189.0	185.8	181.2	178.0
80°	87.5	103.1	112.4	118.7	128.1	132.7	137.4	139.0	135.9	134.3	129.6
82.5°	57.8	62.5	67.2	75.0	85.9	93.7	93.7	92.1	95.3	93.7	92.1
85°	32.8	35.9	37.5	39.0	45.3	53.1	54.7	56.2	59.3	56.2	53.1
87.5°	12.5	14.1	14.1	14.1	17.2	18.7	23.4	29.7	28.1	25.0	25.0
90°	8.7	7.0	6.2	5.6	4.3	3.1	1.8	0.6	1.8	3.1	4.3
92.5°	11.3	10.2	9.6	10.0	10.7	11.5	12.2	13.0	12.2	11.5	10.7
95°	13.4	12.0	11.3	13.9	19.1	24.2	29.4	34.6	29.4	24.2	19.1
97.5°	37.4	43.8	47.0	48.8	52.3	55.8	59.4	62.9	59.4	55.8	52.3
100°	77.6	97.3	107.1	105.8	103.3	100.8	98.3	95.8	98.3	100.8	103.3
102.5°	107.6	129.5	140.5	139.7	138.1	136.4	134.8	133.2	134.8	136.4	138.1
105°	158.1	169.4	175.1	174.4	173.0	171.7	170.3	168.9	170.3	171.7	173.0
107.5°	214.8	212.9	212.0	211.4	210.3	209.2	208.0	206.9	208.0	209.2	210.3
110°	251.5	250.1	249.4	248.9	247.9	246.8	245.8	244.8	245.8	246.8	247.9

TEST NUMBER: P1010849

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	287.2	285.8	285.1	284.7	283.8	282.9	282.0	281.1	282.0	282.9	283.8
115°	321.9	320.8	320.2	319.8	319.1	318.3	317.6	316.8	317.6	318.3	319.1
117.5°	356.8	356.2	355.9	355.5	354.6	353.7	352.8	351.9	352.8	353.7	354.6
120°	389.9	389.5	389.3	388.7	387.6	386.5	385.3	384.2	385.3	386.5	387.6
122.5°	421.8	421.3	421.1	420.7	419.8	418.9	418.0	417.1	418.0	418.9	419.8
125°	451.9	451.4	451.1	450.6	449.6	448.6	447.6	446.6	447.6	448.6	449.6
127.5°	481.5	480.9	480.6	480.1	479.1	478.0	477.0	476.0	477.0	478.0	479.1
130°	508.5	508.0	507.8	507.3	506.3	505.2	504.2	503.2	504.2	505.2	506.3
132.5°	534.5	534.1	533.9	533.4	532.4	531.3	530.3	529.3	530.3	531.3	532.4
135°	560.1	559.6	559.4	559.0	558.3	557.5	556.8	556.0	556.8	557.5	558.3
137.5°	583.6	583.3	583.2	582.7	581.7	580.6	579.6	578.6	579.6	580.6	581.7
140°	605.3	604.9	604.7	604.3	603.6	602.8	602.1	601.3	602.1	602.8	603.6
142.5°	626.3	625.9	625.7	625.3	624.6	623.8	623.1	622.3	623.1	623.8	624.6
145°	645.9	645.6	645.5	645.1	644.2	643.3	642.4	641.5	642.4	643.3	644.2
147.5°	663.5	663.2	663.1	662.8	662.1	661.5	660.8	660.2	660.8	661.5	662.1
150°	679.3	679.0	678.9	678.7	678.3	678.0	677.6	677.2	677.6	678.0	678.3
152.5°	693.3	693.2	693.1	693.0	692.9	692.8	692.6	692.5	692.6	692.8	692.9
155°	705.8	705.7	705.6	705.7	706.0	706.2	706.5	706.7	706.5	706.2	706.0
157.5°	717.8	717.9	718.0	718.0	718.0	718.0	718.0	718.0	718.0	718.0	718.0
160°	727.5	727.6	727.7	727.8	727.9	728.0	728.1	728.2	728.1	728.0	727.9
162.5°	736.0	736.1	736.2	736.4	736.8	737.1	737.5	737.9	737.5	737.1	736.8
165°	743.3	743.4	743.5	743.7	744.1	744.4	744.8	745.2	744.8	744.4	744.1
167.5°	749.2	749.2	749.2	749.5	750.0	750.5	751.0	751.5	751.0	750.5	750.0
170°	754.3	754.3	754.3	754.6	755.1	755.6	756.1	756.6	756.1	755.6	755.1
172.5°	757.3	757.2	757.1	757.4	758.1	758.7	759.4	760.0	759.4	758.7	758.1
175°	760.2	760.1	760.0	760.3	760.9	761.6	762.2	762.8	762.2	761.6	760.9
177.5°	761.3	761.2	761.1	761.4	762.0	762.7	763.3	763.9	763.3	762.7	762.0
180°	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8

TEST NUMBER: P1010849

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1
2.5°	1800.6	1792.8	1789.7	1781.9	1763.1	1750.7	1736.6	1727.2	1728.8	1721.0	1725.7
5°	1744.4	1742.8	1731.9	1716.3	1689.8	1675.7	1650.7	1638.2	1632.0	1633.5	1624.2
7.5°	1697.6	1683.5	1675.7	1650.7	1625.7	1596.0	1575.7	1564.8	1555.4	1546.1	1539.8
10°	1644.5	1632.0	1619.5	1592.9	1558.6	1530.5	1502.3	1491.4	1477.4	1471.1	1466.4
12.5°	1588.2	1580.4	1564.8	1533.6	1494.5	1468.0	1435.2	1428.9	1410.2	1397.7	1394.6
15°	1536.7	1532.0	1503.9	1468.0	1428.9	1402.4	1374.3	1355.5	1324.3	1330.6	1319.6
17.5°	1482.0	1461.7	1444.6	1396.2	1377.4	1336.8	1304.0	1294.6	1272.8	1258.7	1244.7
20°	1421.1	1408.6	1386.8	1355.5	1310.3	1263.4	1238.4	1222.8	1210.3	1188.4	1182.2
22.5°	1363.4	1347.7	1329.0	1288.4	1249.4	1210.3	1176.0	1161.9	1146.3	1130.7	1121.3
25°	1318.1	1294.6	1274.3	1224.4	1185.3	1152.5	1130.7	1107.2	1085.4	1076.0	1072.9
27.5°	1247.8	1233.7	1213.4	1166.6	1130.7	1094.7	1074.4	1058.8	1035.4	1024.5	1015.1
30°	1202.5	1174.4	1151.0	1113.5	1077.6	1038.5	1019.8	1001.0	987.0	972.9	962.0
32.5°	1141.6	1119.7	1101.0	1063.5	1027.6	991.7	971.4	943.3	935.5	924.5	912.0
35°	1082.3	1068.2	1047.9	1007.3	968.2	943.3	921.4	894.8	885.5	877.7	866.7
37.5°	1026.0	1005.7	991.7	952.6	918.3	888.6	871.4	849.6	843.3	833.9	826.1
40°	977.6	957.3	943.3	904.2	868.3	837.1	826.1	804.3	794.9	784.0	779.3
42.5°	923.0	905.8	887.0	858.9	821.4	790.2	768.4	755.9	743.4	738.7	729.3
45°	865.2	849.6	835.5	804.3	765.2	743.4	724.6	707.4	698.1	690.3	684.0
47.5°	815.2	801.1	782.4	748.1	716.8	696.5	677.8	660.6	651.2	641.9	634.0
50°	757.4	749.6	729.3	696.5	666.8	643.4	626.2	610.6	604.4	593.4	580.9
52.5°	705.9	691.8	674.7	648.1	621.6	593.4	570.0	560.6	549.7	543.5	532.5
55°	645.0	635.6	616.9	593.4	565.3	541.9	524.7	512.2	498.2	491.9	477.9
57.5°	593.4	576.3	566.9	537.2	510.7	487.2	474.8	462.3	446.6	437.3	431.0
60°	537.2	521.6	507.5	482.6	463.8	438.8	420.1	409.2	398.2	385.7	379.5
62.5°	482.6	470.1	452.9	432.6	409.2	388.9	374.8	359.2	352.9	340.4	335.8
65°	423.2	413.8	399.8	376.4	357.6	340.4	326.4	313.9	307.7	303.0	299.8
67.5°	370.1	357.6	348.3	328.0	307.7	293.6	285.8	278.0	270.2	265.5	260.8
70°	315.5	306.1	296.7	278.0	263.9	251.4	245.2	238.9	234.3	229.6	224.9
72.5°	259.2	254.6	245.2	232.7	221.8	212.4	207.7	199.9	195.2	187.4	184.3
75°	214.0	206.1	201.5	190.5	181.2	173.3	167.1	157.7	151.5	148.4	146.8
77.5°	168.7	165.5	159.3	149.9	145.2	137.4	128.1	124.9	121.8	121.8	120.3
80°	126.5	121.8	117.1	109.3	104.6	98.4	98.4	98.4	96.8	98.4	96.8
82.5°	85.9	82.8	79.6	75.0	73.4	73.4	75.0	75.0	75.0	75.0	75.0
85°	50.0	50.0	50.0	51.5	50.0	50.0	51.5	53.1	51.5	51.5	50.0
87.5°	23.4	23.4	25.0	25.0	26.5	26.5	26.5	26.5	26.5	26.5	28.1
90°	5.6	6.2	7.0	8.7	10.3	12.0	13.6	14.1	14.6	15.1	15.6
92.5°	10.0	9.6	10.2	11.3	12.4	13.6	14.7	15.6	16.5	17.4	18.3
95°	13.9	11.3	12.0	13.4	14.8	16.2	17.6	18.5	19.3	20.2	21.1
97.5°	48.8	47.0	43.8	37.4	30.9	24.5	18.1	19.1	20.1	21.2	22.2
100°	105.8	107.1	97.3	77.6	58.0	38.3	18.7	19.7	20.7	21.7	22.7
102.5°	139.7	140.5	129.5	107.6	85.7	63.8	41.9	37.7	33.6	29.4	25.3
105°	174.4	175.1	169.4	158.1	146.8	135.4	124.1	101.8	79.5	57.2	34.9
107.5°	211.4	212.0	212.9	214.8	216.7	218.6	220.5	201.1	181.7	162.3	142.9
110°	248.9	249.4	250.1	251.5	252.8	254.2	255.6	251.4	247.3	243.1	239.0

TEST NUMBER: P1010849

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	284.7	285.1	285.8	287.2	288.5	289.9	291.3	292.4	293.6	294.7	295.8
115°	319.8	320.2	320.8	321.9	323.0	324.2	325.3	326.6	327.8	329.1	330.4
117.5°	355.5	355.9	356.2	356.8	357.5	358.1	358.7	359.7	360.7	361.8	362.8
120°	388.7	389.3	389.5	389.9	390.2	390.6	391.0	392.0	393.0	394.1	395.1
122.5°	420.7	421.1	421.3	421.8	422.3	422.8	423.3	423.9	424.6	425.2	425.9
125°	450.6	451.1	451.4	451.9	452.4	452.9	453.4	453.6	453.9	454.1	454.4
127.5°	480.1	480.6	480.9	481.5	482.2	482.8	483.4	483.8	484.2	484.5	484.9
130°	507.3	507.8	508.0	508.5	509.0	509.5	510.0	510.5	511.0	511.5	512.0
132.5°	533.4	533.9	534.1	534.5	534.8	535.2	535.6	536.1	536.6	537.1	537.6
135°	559.0	559.4	559.6	560.1	560.6	561.1	561.6	562.0	562.4	562.7	563.1
137.5°	582.7	583.2	583.3	583.6	583.8	584.1	584.3	584.9	585.5	586.2	586.8
140°	604.3	604.7	604.9	605.3	605.6	606.0	606.4	606.9	607.4	607.9	608.4
142.5°	625.3	625.7	625.9	626.3	626.6	627.0	627.4	627.8	628.2	628.5	628.9
145°	645.1	645.5	645.6	645.9	646.1	646.4	646.6	646.9	647.1	647.4	647.7
147.5°	662.8	663.1	663.2	663.5	663.7	664.0	664.2	664.4	664.7	664.9	665.2
150°	678.7	678.9	679.0	679.3	679.6	679.8	680.1	680.3	680.6	680.8	681.1
152.5°	693.0	693.1	693.2	693.3	693.4	693.6	693.7	694.2	694.7	695.2	695.7
155°	705.7	705.6	705.7	705.8	705.9	706.0	706.1	706.7	707.4	708.0	708.7
157.5°	718.0	718.0	717.9	717.8	717.7	717.6	717.5	718.3	719.0	719.8	720.5
160°	727.8	727.7	727.6	727.5	727.4	727.2	727.1	727.9	728.6	729.4	730.1
162.5°	736.4	736.2	736.1	736.0	735.9	735.7	735.6	736.5	737.4	738.3	739.2
165°	743.7	743.5	743.4	743.3	743.2	743.1	743.0	744.0	745.0	746.0	747.0
167.5°	749.5	749.2	749.2	749.2	749.2	749.2	749.2	750.2	751.2	752.2	753.2
170°	754.6	754.3	754.3	754.3	754.3	754.3	754.3	755.3	756.3	757.3	758.3
172.5°	757.4	757.1	757.2	757.3	757.4	757.6	757.7	758.7	759.7	760.7	761.7
175°	760.3	760.0	760.1	760.2	760.3	760.4	760.5	761.4	762.3	763.2	764.1
177.5°	761.4	761.1	761.2	761.3	761.4	761.6	761.7	762.7	763.7	764.7	765.7
180°	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8

TEST NUMBER: P1010849

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1
2.5°	1724.1	1725.7	1721.0	1711.6	1710.1	1713.2	1722.5	1719.4	1711.6	1725.7	1713.2
5°	1628.8	1621.0	1617.9	1621.0	1611.7	1607.0	1616.4	1611.7	1616.4	1617.9	1622.6
7.5°	1536.7	1538.3	1528.9	1530.5	1518.0	1521.1	1521.1	1521.1	1525.8	1528.9	1535.1
10°	1457.1	1460.2	1449.2	1450.8	1441.4	1435.2	1439.9	1449.2	1449.2	1449.2	1452.4
12.5°	1393.0	1379.0	1371.2	1369.6	1358.7	1355.5	1364.9	1368.0	1375.9	1375.9	1380.5
15°	1313.4	1310.3	1304.0	1304.0	1277.5	1283.7	1286.8	1297.8	1313.4	1300.9	1304.0
17.5°	1241.5	1233.7	1225.9	1222.8	1219.7	1210.3	1222.8	1221.2	1230.6	1232.2	1236.9
20°	1177.5	1171.3	1155.7	1157.2	1160.3	1146.3	1154.1	1154.1	1163.5	1172.8	1183.8
22.5°	1115.0	1108.8	1101.0	1104.1	1094.7	1091.6	1091.6	1099.4	1110.4	1118.2	1116.6
25°	1066.6	1055.7	1051.0	1046.3	1041.6	1044.8	1040.1	1047.9	1055.7	1060.4	1055.7
27.5°	1012.0	1007.3	997.9	993.2	985.4	988.6	991.7	997.9	1002.6	1002.6	1007.3
30°	958.9	952.6	949.5	944.8	944.8	938.6	940.1	946.4	951.1	955.8	962.0
32.5°	907.3	902.7	898.0	898.0	894.8	893.3	891.7	901.1	901.1	910.5	910.5
35°	865.2	857.4	857.4	849.6	852.7	851.1	848.0	854.2	855.8	862.1	860.5
37.5°	818.3	818.3	815.2	807.4	801.1	802.7	810.5	810.5	815.2	813.6	818.3
40°	771.5	768.4	768.4	763.7	762.1	760.5	762.1	763.7	771.5	769.9	771.5
42.5°	724.6	726.2	718.4	718.4	718.4	713.7	715.3	716.8	719.9	723.1	727.7
45°	679.3	676.2	674.7	671.5	668.4	670.0	668.4	674.7	673.1	676.2	680.9
47.5°	630.9	626.2	624.7	618.4	618.4	621.6	620.0	624.7	626.2	630.9	627.8
50°	584.1	577.8	573.1	574.7	565.3	568.5	568.5	573.1	577.8	579.4	582.5
52.5°	529.4	527.9	526.3	518.5	516.9	515.4	516.9	518.5	524.7	529.4	531.0
55°	476.3	474.8	465.4	462.3	457.6	457.6	460.7	462.3	473.2	474.8	481.0
57.5°	427.9	423.2	412.3	410.7	410.7	410.7	406.0	412.3	415.4	423.2	423.2
60°	374.8	374.8	365.4	365.4	367.0	365.4	365.4	367.0	367.0	373.2	376.4
62.5°	332.6	331.1	331.1	328.0	326.4	328.0	326.4	326.4	328.0	332.6	337.3
65°	295.2	293.6	292.0	290.5	287.4	287.4	288.9	292.0	292.0	295.2	296.7
67.5°	259.2	259.2	256.1	256.1	254.6	253.0	254.6	253.0	259.2	259.2	260.8
70°	223.3	221.8	217.1	215.5	210.8	212.4	212.4	217.1	218.6	221.8	224.9
72.5°	179.6	179.6	176.5	173.3	174.9	171.8	171.8	173.3	173.3	178.0	179.6
75°	148.4	145.2	143.7	145.2	143.7	146.8	143.7	143.7	146.8	146.8	146.8
77.5°	121.8	121.8	120.3	120.3	121.8	120.3	121.8	121.8	121.8	120.3	121.8
80°	99.9	98.4	98.4	98.4	96.8	96.8	96.8	96.8	96.8	96.8	96.8
82.5°	75.0	75.0	73.4	75.0	75.0	73.4	75.0	73.4	73.4	75.0	75.0
85°	50.0	53.1	50.0	50.0	51.5	51.5	53.1	51.5	53.1	50.0	51.5
87.5°	26.5	28.1	28.1	26.5	26.5	28.1	28.1	28.1	29.7	26.5	28.1
90°	15.9	16.0	16.3	16.5	16.8	17.0	16.8	16.5	16.3	16.0	15.9
92.5°	18.7	18.8	18.9	19.0	19.2	19.3	19.2	19.0	18.9	18.8	18.7
95°	21.5	21.5	21.5	21.5	21.5	21.5	21.5	21.5	21.5	21.5	21.5
97.5°	22.7	22.8	22.9	23.0	23.1	23.2	23.1	23.0	22.9	22.8	22.7
100°	23.2	23.3	23.4	23.5	23.7	23.8	23.7	23.5	23.4	23.3	23.2
102.5°	23.2	23.3	23.6	23.9	24.1	24.4	24.1	23.9	23.6	23.3	23.2
105°	23.8	23.9	24.2	24.4	24.7	24.9	24.7	24.4	24.2	23.9	23.8
107.5°	133.2	124.9	108.4	91.9	75.4	58.9	75.4	91.9	108.4	124.9	133.2
110°	236.9	227.9	209.9	191.8	173.8	155.8	173.8	191.8	209.9	227.9	236.9

TEST NUMBER: P1010849

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	296.4	296.3	296.0	295.8	295.5	295.3	295.5	295.8	296.0	296.3	296.4
115°	331.0	331.2	331.7	332.2	332.7	333.2	332.7	332.2	331.7	331.2	331.0
117.5°	363.3	363.4	363.5	363.6	363.7	363.8	363.7	363.6	363.5	363.4	363.3
120°	395.6	395.6	395.6	395.6	395.6	395.6	395.6	395.6	395.6	395.6	395.6
122.5°	426.2	426.3	426.4	426.5	426.6	426.7	426.6	426.5	426.4	426.3	426.2
125°	454.5	454.6	454.9	455.1	455.4	455.6	455.4	455.1	454.9	454.6	454.5
127.5°	485.1	485.0	484.7	484.5	484.2	484.0	484.2	484.5	484.7	485.0	485.1
130°	512.3	512.2	511.9	511.7	511.4	511.2	511.4	511.7	511.9	512.2	512.3
132.5°	537.8	537.6	537.2	536.9	536.5	536.1	536.5	536.9	537.2	537.6	537.8
135°	563.3	563.1	562.7	562.4	562.0	561.6	562.0	562.4	562.7	563.1	563.3
137.5°	587.1	587.0	586.7	586.5	586.2	586.0	586.2	586.5	586.7	587.0	587.1
140°	608.7	608.6	608.3	608.0	607.8	607.5	607.8	608.0	608.3	608.6	608.7
142.5°	629.1	628.9	628.5	628.2	627.8	627.4	627.8	628.2	628.5	628.9	629.1
145°	647.8	647.8	647.8	647.8	647.8	647.8	647.8	647.8	647.8	647.8	647.8
147.5°	665.3	665.0	664.4	663.7	663.1	662.5	663.1	663.7	664.4	665.0	665.3
150°	681.2	681.0	680.6	680.3	679.9	679.5	679.9	680.3	680.6	681.0	681.2
152.5°	695.9	695.6	695.0	694.3	693.7	693.1	693.7	694.3	695.0	695.6	695.9
155°	709.0	708.6	707.9	707.1	706.4	705.6	706.4	707.1	707.9	708.6	709.0
157.5°	720.9	720.4	719.4	718.3	717.3	716.3	717.3	718.3	719.4	720.4	720.9
160°	730.5	730.1	729.2	728.3	727.4	726.5	727.4	728.3	729.2	730.1	730.5
162.5°	739.6	739.2	738.5	737.7	737.0	736.2	737.0	737.7	738.5	739.2	739.6
165°	747.5	747.1	746.2	745.3	744.4	743.5	744.4	745.3	746.2	747.1	747.5
167.5°	753.7	753.2	752.2	751.2	750.2	749.2	750.2	751.2	752.2	753.2	753.7
170°	758.8	758.3	757.3	756.3	755.3	754.3	755.3	756.3	757.3	758.3	758.8
172.5°	762.2	761.6	760.5	759.4	758.2	757.1	758.2	759.4	760.5	761.6	762.2
175°	764.5	764.0	763.0	762.0	761.0	760.0	761.0	762.0	763.0	764.0	764.5
177.5°	766.2	765.6	764.3	763.0	761.8	760.5	761.8	763.0	764.3	765.6	766.2
180°	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8

TEST NUMBER: P1010849

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1	1824.1
2.5°	1725.7	1731.9	1725.7	1713.2	1725.7	1733.5	1741.3	1753.8	1760.0	1760.0	1769.4
5°	1627.3	1639.8	1635.1	1632.0	1644.5	1652.3	1664.8	1680.4	1697.6	1708.5	1721.0
7.5°	1539.8	1547.6	1555.4	1555.4	1567.9	1585.1	1603.9	1622.6	1644.5	1660.1	1669.4
10°	1463.3	1469.6	1474.2	1480.5	1499.2	1518.0	1543.0	1566.4	1585.1	1602.3	1617.9
12.5°	1389.9	1399.3	1410.2	1414.9	1428.9	1452.4	1475.8	1503.9	1533.6	1550.8	1566.4
15°	1319.6	1324.3	1336.8	1350.9	1363.4	1388.3	1418.0	1447.7	1472.7	1499.2	1513.3
17.5°	1247.8	1249.4	1282.1	1274.3	1314.9	1338.4	1354.0	1382.1	1422.7	1444.6	1466.4
20°	1177.5	1193.1	1207.2	1215.0	1236.9	1263.4	1308.7	1330.6	1363.4	1383.7	1402.4
22.5°	1122.9	1146.3	1146.3	1165.0	1176.0	1200.9	1233.7	1275.9	1311.8	1325.9	1352.4
25°	1074.4	1085.4	1104.1	1110.4	1130.7	1152.5	1174.4	1219.7	1258.7	1277.5	1296.2
27.5°	1012.0	1026.0	1051.0	1051.0	1077.6	1101.0	1127.5	1157.2	1196.3	1222.8	1243.1
30°	963.6	977.6	988.6	1005.7	1016.7	1038.5	1085.4	1107.2	1141.6	1165.0	1190.0
32.5°	918.3	929.2	938.6	957.3	969.8	994.8	1019.8	1058.8	1088.5	1110.4	1136.9
35°	868.3	879.2	891.7	905.8	924.5	947.9	971.4	1004.2	1033.8	1054.1	1076.0
37.5°	821.4	829.3	848.0	857.4	873.0	894.8	924.5	958.9	985.4	1001.0	1022.9
40°	776.2	782.4	796.5	813.6	824.6	841.8	873.0	902.7	935.5	954.2	971.4
42.5°	727.7	735.6	748.1	765.2	782.4	801.1	818.3	852.7	882.4	898.0	916.7
45°	685.6	690.3	699.6	716.8	734.0	748.1	774.6	805.8	833.9	846.4	866.7
47.5°	635.6	640.3	654.3	662.2	680.9	699.6	726.2	757.4	782.4	794.9	813.6
50°	584.1	588.8	598.1	615.3	627.8	648.1	671.5	698.1	729.3	746.5	757.4
52.5°	534.1	543.5	551.3	565.3	580.9	601.3	623.1	648.1	674.7	691.8	704.3
55°	484.1	491.9	501.3	509.1	527.9	546.6	571.6	595.0	618.4	634.0	648.1
57.5°	427.9	438.8	448.2	463.8	477.9	493.5	521.6	540.3	568.5	579.4	591.9
60°	379.5	390.4	398.2	410.7	423.2	443.5	462.3	485.7	509.1	523.2	538.8
62.5°	338.9	343.6	348.3	360.8	373.2	392.0	410.7	434.2	459.1	466.9	479.4
65°	298.3	303.0	310.8	321.7	331.1	342.0	362.3	381.1	404.5	417.0	421.7
67.5°	263.9	268.6	270.2	278.0	285.8	298.3	309.2	328.0	349.8	357.6	367.0
70°	224.9	232.7	234.3	240.5	243.6	251.4	263.9	278.0	295.2	309.2	317.0
72.5°	179.6	190.5	193.6	203.0	207.7	215.5	224.9	235.8	246.7	253.0	259.2
75°	146.8	149.9	151.5	159.3	167.1	178.0	182.7	189.0	198.3	206.1	212.4
77.5°	121.8	123.4	124.9	124.9	126.5	132.7	142.1	149.9	156.2	159.3	164.0
80°	98.4	96.8	96.8	98.4	98.4	98.4	101.5	112.4	115.6	123.4	121.8
82.5°	76.5	73.4	75.0	73.4	73.4	73.4	73.4	75.0	75.0	79.6	82.8
85°	50.0	51.5	50.0	50.0	48.4	50.0	48.4	48.4	46.9	46.9	45.3
87.5°	26.5	28.1	26.5	26.5	25.0	26.5	25.0	25.0	23.4	23.4	20.3
90°	15.6	15.1	14.6	14.1	13.6	12.0	10.3	8.7	7.0	6.2	5.6
92.5°	18.3	17.4	16.5	15.6	14.7	13.6	12.4	11.3	10.2	9.6	10.0
95°	21.1	20.2	19.3	18.5	17.6	16.2	14.8	13.4	12.0	11.3	13.9
97.5°	22.2	21.2	20.1	19.1	18.1	24.5	30.9	37.4	43.8	47.0	48.8
100°	22.7	21.7	20.7	19.7	18.7	38.3	58.0	77.6	97.3	107.1	105.8
102.5°	25.3	29.4	33.6	37.7	41.9	63.8	85.7	107.6	129.5	140.5	139.7
105°	34.9	57.2	79.5	101.8	124.1	135.4	146.8	158.1	169.4	175.1	174.4
107.5°	142.9	162.3	181.7	201.1	220.5	218.6	216.7	214.8	212.9	212.0	211.4
110°	239.0	243.1	247.3	251.4	255.6	254.2	252.8	251.5	250.1	249.4	248.9

TEST NUMBER: P1010849

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	295.8	294.7	293.6	292.4	291.3	289.9	288.5	287.2	285.8	285.1	284.7
115°	330.4	329.1	327.8	326.6	325.3	324.2	323.0	321.9	320.8	320.2	319.8
117.5°	362.8	361.8	360.7	359.7	358.7	358.1	357.5	356.8	356.2	355.9	355.5
120°	395.1	394.1	393.0	392.0	391.0	390.6	390.2	389.9	389.5	389.3	388.7
122.5°	425.9	425.2	424.6	423.9	423.3	422.8	422.3	421.8	421.3	421.1	420.7
125°	454.4	454.1	453.9	453.6	453.4	452.9	452.4	451.9	451.4	451.1	450.6
127.5°	484.9	484.5	484.2	483.8	483.4	482.8	482.2	481.5	480.9	480.6	480.1
130°	512.0	511.5	511.0	510.5	510.0	509.5	509.0	508.5	508.0	507.8	507.3
132.5°	537.6	537.1	536.6	536.1	535.6	535.2	534.8	534.5	534.1	533.9	533.4
135°	563.1	562.7	562.4	562.0	561.6	561.1	560.6	560.1	559.6	559.4	559.0
137.5°	586.8	586.2	585.5	584.9	584.3	584.1	583.8	583.6	583.3	583.2	582.7
140°	608.4	607.9	607.4	606.9	606.4	606.0	605.6	605.3	604.9	604.7	604.3
142.5°	628.9	628.5	628.2	627.8	627.4	627.0	626.6	626.3	625.9	625.7	625.3
145°	647.7	647.4	647.1	646.9	646.6	646.4	646.1	645.9	645.6	645.5	645.1
147.5°	665.2	664.9	664.7	664.4	664.2	664.0	663.7	663.5	663.2	663.1	662.8
150°	681.1	680.8	680.6	680.3	680.1	679.8	679.6	679.3	679.0	678.9	678.7
152.5°	695.7	695.2	694.7	694.2	693.7	693.6	693.4	693.3	693.2	693.1	693.0
155°	708.7	708.0	707.4	706.7	706.1	706.0	705.9	705.8	705.7	705.6	705.7
157.5°	720.5	719.8	719.0	718.3	717.5	717.6	717.7	717.8	717.9	718.0	718.0
160°	730.1	729.4	728.6	727.9	727.1	727.2	727.4	727.5	727.6	727.7	727.8
162.5°	739.2	738.3	737.4	736.5	735.6	735.7	735.9	736.0	736.1	736.2	736.4
165°	747.0	746.0	745.0	744.0	743.0	743.1	743.2	743.3	743.4	743.5	743.7
167.5°	753.2	752.2	751.2	750.2	749.2	749.2	749.2	749.2	749.2	749.2	749.5
170°	758.3	757.3	756.3	755.3	754.3	754.3	754.3	754.3	754.3	754.3	754.6
172.5°	761.7	760.7	759.7	758.7	757.7	757.6	757.4	757.3	757.2	757.1	757.4
175°	764.1	763.2	762.3	761.4	760.5	760.4	760.3	760.2	760.1	760.0	760.3
177.5°	765.7	764.7	763.7	762.7	761.7	761.6	761.4	761.3	761.2	761.1	761.4
180°	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8	762.8

TEST NUMBER: P1010849

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1824.1	1824.1	1824.1	1824.1
2.5°	1777.2	1788.1	1810.0	1828.7
5°	1739.7	1756.9	1789.7	1822.5
7.5°	1694.4	1721.0	1763.1	1808.4
10°	1650.7	1685.1	1736.6	1789.7
12.5°	1607.0	1642.9	1697.6	1766.3
15°	1555.4	1592.9	1658.5	1741.3
17.5°	1510.2	1560.1	1619.5	1702.2
20°	1461.7	1499.2	1575.7	1663.2
22.5°	1400.8	1463.3	1535.1	1627.3
25°	1352.4	1407.1	1478.9	1583.6
27.5°	1293.1	1357.1	1444.6	1536.7
30°	1244.7	1297.8	1379.0	1489.9
32.5°	1188.4	1250.9	1335.2	1444.6
35°	1138.5	1191.6	1271.2	1382.1
37.5°	1079.1	1136.9	1225.9	1324.3
40°	1027.6	1083.8	1168.1	1260.3
42.5°	965.1	1024.5	1108.8	1186.9
45°	915.2	969.8	1037.0	1108.8
47.5°	854.2	912.0	977.6	1027.6
50°	799.6	852.7	904.2	946.4
52.5°	740.2	788.7	835.5	866.7
55°	685.6	723.1	760.5	782.4
57.5°	621.6	657.5	688.7	701.2
60°	565.3	595.0	615.3	629.4
62.5°	506.0	527.9	543.5	551.3
65°	448.2	463.8	471.6	479.4
67.5°	388.9	402.9	407.6	417.0
70°	326.4	342.0	345.1	349.8
72.5°	279.5	279.5	285.8	292.0
75°	223.3	226.4	229.6	229.6
77.5°	174.9	174.9	178.0	179.6
80°	128.1	129.6	129.6	128.1
82.5°	87.5	90.6	87.5	85.9
85°	48.4	54.7	51.5	51.5
87.5°	20.3	20.3	23.4	20.3
90°	4.3	3.1	1.8	0.6
92.5°	10.7	11.5	12.2	13.0
95°	19.1	24.2	29.4	34.6
97.5°	52.3	55.8	59.4	62.9
100°	103.3	100.8	98.3	95.8
102.5°	138.1	136.4	134.8	133.2
105°	173.0	171.7	170.3	168.9
107.5°	210.3	209.2	208.0	206.9
110°	247.9	246.8	245.8	244.8

TEST NUMBER: P1010849

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	283.8	282.9	282.0	281.1
115°	319.1	318.3	317.6	316.8
117.5°	354.6	353.7	352.8	351.9
120°	387.6	386.5	385.3	384.2
122.5°	419.8	418.9	418.0	417.1
125°	449.6	448.6	447.6	446.6
127.5°	479.1	478.0	477.0	476.0
130°	506.3	505.2	504.2	503.2
132.5°	532.4	531.3	530.3	529.3
135°	558.3	557.5	556.8	556.0
137.5°	581.7	580.6	579.6	578.6
140°	603.6	602.8	602.1	601.3
142.5°	624.6	623.8	623.1	622.3
145°	644.2	643.3	642.4	641.5
147.5°	662.1	661.5	660.8	660.2
150°	678.3	678.0	677.6	677.2
152.5°	692.9	692.8	692.6	692.5
155°	706.0	706.2	706.5	706.7
157.5°	718.0	718.0	718.0	718.0
160°	727.9	728.0	728.1	728.2
162.5°	736.8	737.1	737.5	737.9
165°	744.1	744.4	744.8	745.2
167.5°	750.0	750.5	751.0	751.5
170°	755.1	755.6	756.1	756.6
172.5°	758.1	758.7	759.4	760.0
175°	760.9	761.6	762.2	762.8
177.5°	762.0	762.7	763.3	763.9
180°	762.8	762.8	762.8	762.8

(END OF REPORT)