

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010913

Luminaire Tested: S123RDIP-B340D805UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010913
REPORT IS A COMBINATION OF REPORTS P993289 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D805UB2750-4F0-XX-W2A-A_5000K
Description: Define 3 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4283.0 lumens
Efficiency: N/A
Efficacy: 125.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010913

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010913

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	94	90	86	83	84	80	77	75	64	61	60	48	47	46	34	33	32
2	85	79	73	68	76	71	66	62	56	53	50	42	40	39	30	29	28
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24
4	72	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21
5	66	55	47	41	59	50	43	38	40	35	31	30	27	25	22	20	18
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15
8	52	40	33	28	46	36	30	26	29	25	21	23	20	17	17	15	13
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12
10	45	33	27	22	40	30	24	20	25	20	17	19	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5481	5481	5481	5481
5°	5486	6313	5500	4683
10°	5437	7621	5461	4091
15°	5381	8649	5381	3607
20°	5270	9329	5300	3200
25°	5190	8864	5180	2920
30°	5096	6141	5086	2645
35°	4982	3943	4960	2439
40°	4842	2784	4818	2233
45°	4596	2228	4591	2033
50°	4296	1864	4282	1800
55°	3957	1536	3926	1525
60°	3625	1269	3590	1297
65°	3234	1016	3256	1100
70°	2877	706	2954	889
75°	2438	524	2537	684
80°	1944	347	2106	512
85°	1383	164	1508	319

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 7318 cd/sqm

TEST NUMBER: P1010913

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	1.2
10°-20°	156.5	3.7
20°-30°	246.6	5.8
30°-40°	256.4	6.0
40°-50°	219.3	5.1
50°-60°	167.2	3.9
60°-70°	107.1	2.5
70°-80°	51.3	1.2
80°-90°	15.5	0.4
90°-100°	34.9	0.8
100°-110°	168.5	3.9
110°-120°	412.9	9.6
120°-130°	524.2	12.2
130°-140°	560.0	13.1
140°-150°	523.6	12.2
150°-160°	422.4	9.9
160°-170°	272.6	6.4
170°-180°	93.9	2.2
0°-30°	453.1	10.6
0°-40°	709.5	16.6
0°-60°	1096.0	25.6
0°-90°	1270.0	29.7
90°-120°	616.3	14.4
90°-150°	2224.1	51.9
90°-180°	3013.0	70.3
0°-180°	4283.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	509	509	509	509	509	
5°	509	605	510	449	509	48
15°	486	859	486	358	486	137
25°	442	886	441	292	442	204
35°	386	384	384	238	386	241
45°	310	205	309	187	310	238
55°	218	129	217	128	218	196
65°	134	74	135	80	134	134
75°	64	31	67	41	64	69
85°	14	7	16	14	14	16
90°	1	22	1	22	1	3
95°	45	28	45	28	45	54
105°	219	32	219	32	219	232
115°	410	432	410	432	410	405
125°	579	590	579	590	579	517
135°	720	728	720	728	720	555
145°	831	839	831	839	831	520
155°	916	914	916	914	916	422
165°	966	963	966	963	966	273
175°	988	985	988	985	988	94
180°	988	988	988	988	988	

TEST NUMBER: P1010913

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	510.5	514.0	516.6	518.4	522.7	525.4	527.5	531.5	531.5	532.3	534.1
5°	508.8	516.2	521.4	528.4	537.6	541.9	548.0	553.3	560.7	564.6	568.5
7.5°	504.9	515.3	526.2	536.7	550.2	558.9	565.0	578.5	588.1	599.9	609.1
10°	499.6	514.0	528.0	544.1	562.4	575.5	584.7	602.5	620.8	637.4	651.4
12.5°	493.1	510.5	530.6	550.2	575.9	589.0	603.8	626.1	652.2	673.2	691.9
15°	486.1	506.2	528.8	552.8	585.1	603.4	624.8	651.8	681.0	711.1	736.8
17.5°	475.2	500.5	525.8	560.7	598.6	609.5	627.8	664.9	701.1	728.1	759.5
20°	464.3	492.7	524.5	555.9	596.9	622.1	639.1	678.4	717.2	749.9	780.0
22.5°	454.3	483.9	517.1	556.7	595.1	620.4	641.8	682.7	727.7	764.3	801.3
25°	442.1	474.3	511.0	548.5	595.1	614.3	637.8	685.4	732.9	775.2	821.0
27.5°	429.0	461.7	497.9	536.3	579.0	607.3	630.4	681.4	739.4	784.8	831.9
30°	415.9	449.5	484.4	518.8	566.8	593.8	620.4	676.6	742.9	794.8	831.0
32.5°	403.3	431.6	466.1	499.6	547.2	576.8	606.9	671.8	744.2	787.8	805.3
35°	385.8	415.5	443.4	479.1	527.1	556.3	591.6	671.4	738.6	765.6	756.9
37.5°	369.7	394.6	421.2	453.0	502.2	540.2	576.8	660.1	719.8	721.5	672.3
40°	351.8	372.3	394.6	428.1	481.3	518.8	558.5	642.6	685.8	660.1	573.3
42.5°	331.3	349.7	367.1	399.8	457.8	499.6	542.4	620.8	636.5	577.2	487.0
45°	309.5	324.4	340.5	374.9	432.9	474.3	517.1	587.3	571.1	487.4	401.5
47.5°	286.9	299.5	315.2	346.6	406.3	448.6	489.2	539.3	498.3	408.5	336.6
50°	264.2	274.2	289.5	321.8	379.3	417.7	455.2	487.9	430.3	350.5	278.2
52.5°	242.0	249.8	265.5	293.0	348.8	385.4	412.4	425.1	366.7	289.5	241.5
55°	218.4	227.1	237.6	265.5	320.9	347.9	365.8	365.4	305.2	245.5	199.7
57.5°	195.8	203.6	212.8	240.7	285.6	303.9	319.1	311.7	254.6	201.0	171.3
60°	175.7	180.1	190.1	213.6	247.6	263.3	272.1	259.4	208.0	169.6	141.7
62.5°	153.9	158.3	166.5	188.8	209.7	218.0	225.4	209.3	171.8	138.2	121.2
65°	133.8	139.5	144.7	162.6	174.0	184.0	183.1	169.6	134.3	112.5	98.5
67.5°	116.4	118.6	122.9	133.8	139.1	146.5	146.9	131.7	108.1	91.6	83.3
70°	97.7	99.8	102.9	108.1	111.6	113.4	112.5	99.0	81.5	71.5	64.1
72.5°	81.5	81.1	83.3	83.3	86.8	86.3	83.7	73.2	61.9	53.6	49.3
75°	64.1	64.5	65.0	64.1	62.8	61.0	58.9	51.0	43.6	39.7	35.8
77.5°	50.1	49.3	49.7	46.6	44.9	43.2	40.1	36.2	30.1	29.2	27.5
80°	35.8	35.3	34.9	33.6	29.6	27.9	25.7	23.5	22.2	21.4	20.9
82.5°	24.0	24.0	23.1	20.5	18.3	17.0	16.6	15.7	14.4	14.4	14.0
85°	14.4	14.0	13.1	10.5	9.2	9.2	9.2	9.2	8.3	8.3	7.8
87.5°	5.7	5.2	3.9	3.9	3.5	3.5	3.5	3.1	3.1	2.6	2.6
90°	0.7	2.3	4.0	5.6	7.3	8.1	9.2	11.3	13.4	15.5	17.6
92.5°	16.9	15.9	14.9	14.0	13.0	12.5	13.2	14.7	16.2	17.6	19.1
95°	44.8	38.1	31.4	24.7	18.0	14.7	15.6	17.4	19.2	21.0	22.8
97.5°	81.5	76.9	72.3	67.8	63.2	60.9	56.7	48.4	40.1	31.8	23.5
100°	124.1	127.4	130.6	133.9	137.2	138.8	126.1	100.6	75.1	49.7	24.2
102.5°	172.6	174.7	176.8	178.9	181.0	182.1	167.9	139.5	111.1	82.7	54.3
105°	218.8	220.6	222.4	224.2	226.0	226.9	219.6	204.9	190.2	175.5	160.8
107.5°	268.0	269.5	270.9	272.4	273.9	274.6	275.8	278.3	280.7	283.2	285.6
110°	317.2	318.5	319.8	321.1	322.4	323.1	324.0	325.8	327.6	329.4	331.2

TEST NUMBER: P1010913

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	364.2	365.3	366.5	367.6	368.7	369.3	370.2	372.0	373.8	375.6	377.4
115°	410.5	411.5	412.5	413.4	414.4	414.9	415.6	417.1	418.6	420.0	421.5
117.5°	456.0	457.1	458.3	459.4	460.5	461.1	461.5	462.3	463.2	464.0	464.8
120°	497.8	499.3	500.7	502.2	503.7	504.4	504.7	505.2	505.7	506.2	506.7
122.5°	540.4	541.6	542.7	543.9	545.0	545.6	545.9	546.6	547.2	547.9	548.5
125°	578.6	579.9	581.2	582.5	583.8	584.5	584.8	585.5	586.1	586.8	587.4
127.5°	616.8	618.1	619.4	620.7	622.0	622.7	623.1	623.9	624.7	625.5	626.3
130°	652.0	653.3	654.6	655.9	657.2	657.9	658.2	658.9	659.5	660.2	660.8
132.5°	685.8	687.1	688.4	689.7	691.0	691.7	691.9	692.4	692.9	693.4	693.9
135°	720.3	721.3	722.3	723.2	724.2	724.7	725.0	725.7	726.4	727.0	727.7
137.5°	749.7	751.0	752.3	753.6	754.9	755.6	755.8	756.1	756.4	756.7	757.0
140°	779.1	780.1	781.1	782.0	783.0	783.5	783.7	784.2	784.7	785.2	785.7
142.5°	806.2	807.2	808.2	809.1	810.1	810.6	810.8	811.3	811.8	812.3	812.8
145°	831.2	832.3	833.5	834.6	835.7	836.3	836.5	836.8	837.1	837.5	837.8
147.5°	855.4	856.2	857.0	857.9	858.7	859.1	859.3	859.6	859.9	860.3	860.6
150°	877.5	878.0	878.5	879.0	879.5	879.7	879.9	880.2	880.5	880.8	881.1
152.5°	897.3	897.5	897.6	897.8	897.9	898.0	898.1	898.3	898.4	898.6	898.8
155°	915.6	915.3	915.0	914.7	914.4	914.2	914.3	914.4	914.6	914.7	914.9
157.5°	930.3	930.3	930.3	930.3	930.3	930.3	930.2	930.1	929.9	929.8	929.6
160°	943.5	943.3	943.2	943.0	942.9	942.8	942.7	942.6	942.4	942.3	942.1
162.5°	956.0	955.5	955.0	954.5	954.0	953.8	953.7	953.6	953.4	953.3	953.1
165°	965.6	965.1	964.6	964.1	963.6	963.4	963.3	963.1	963.0	962.8	962.6
167.5°	973.7	973.0	972.4	971.7	971.0	970.7	970.7	970.7	970.7	970.7	970.7
170°	980.3	979.6	979.0	978.3	977.6	977.3	977.3	977.3	977.3	977.3	977.3
172.5°	984.7	983.9	983.1	982.2	981.4	981.0	981.1	981.2	981.4	981.5	981.7
175°	988.3	987.5	986.7	985.9	985.1	984.7	984.8	984.9	985.1	985.2	985.4
177.5°	989.8	989.0	988.2	987.3	986.5	986.1	986.2	986.4	986.5	986.7	986.9
180°	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3

TEST NUMBER: P1010913

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	537.6	537.6	541.5	545.4	543.2	544.5	549.3	547.6	551.1	550.6	552.0
5°	578.1	582.9	586.8	595.1	596.4	595.1	603.4	605.6	609.5	604.7	606.9
7.5°	623.9	633.9	643.5	655.7	659.6	660.5	664.9	671.0	676.2	666.6	671.4
10°	668.4	683.6	703.2	714.1	723.7	727.2	730.7	734.6	740.7	746.4	742.0
12.5°	716.3	738.6	757.3	776.9	788.7	787.4	797.4	800.0	804.8	806.1	807.9
15°	755.6	786.9	798.7	827.9	830.5	839.3	850.6	860.6	861.9	859.3	859.3
17.5°	793.0	820.1	841.0	864.6	869.3	876.8	891.1	895.9	897.7	897.2	897.2
20°	823.6	841.4	876.8	896.4	904.2	913.8	923.8	929.9	931.3	933.0	930.4
22.5°	843.6	870.7	899.4	915.6	922.1	925.6	932.1	933.9	931.7	932.1	932.6
25°	859.3	885.9	903.4	907.7	907.3	902.9	898.1	889.8	889.0	885.5	878.5
27.5°	863.7	873.7	871.5	853.7	835.8	834.0	805.3	789.6	771.7	774.3	764.3
30°	840.1	827.1	796.1	750.8	732.0	701.5	669.2	635.7	622.6	608.2	634.8
32.5°	782.6	735.9	681.0	622.1	590.8	563.7	529.3	504.9	490.9	479.1	501.8
35°	695.8	623.0	550.2	494.4	468.7	444.3	412.0	399.8	382.4	384.1	386.3
37.5°	584.2	504.0	449.1	394.1	377.1	367.1	343.6	324.8	318.7	317.0	317.0
40°	479.6	413.7	364.9	321.8	308.7	300.4	281.6	272.9	266.4	264.6	266.8
42.5°	396.7	340.5	302.6	273.8	264.6	254.2	246.3	235.4	234.1	231.1	235.0
45°	333.1	284.3	255.9	235.0	227.1	223.2	214.5	208.0	205.3	204.9	208.0
47.5°	282.5	244.6	219.7	206.7	200.6	196.6	189.2	186.6	184.0	184.9	183.5
50°	237.2	208.8	192.7	180.9	177.0	173.1	168.3	165.7	164.4	164.4	163.9
52.5°	203.6	180.1	169.6	158.7	157.0	154.8	149.5	147.8	145.6	145.2	146.9
55°	174.4	158.3	147.8	141.3	139.5	135.2	133.0	130.8	129.5	128.6	129.1
57.5°	149.1	136.9	129.9	124.3	121.2	119.5	115.5	115.1	114.2	114.2	113.8
60°	128.2	119.5	111.2	107.7	105.5	103.3	102.9	100.3	99.0	99.8	99.4
62.5°	108.6	101.6	96.8	92.9	91.6	89.8	88.5	87.6	86.3	86.8	86.8
65°	90.7	85.0	81.5	78.0	77.6	75.9	75.4	74.6	74.6	74.1	75.0
67.5°	74.6	70.6	67.6	65.4	64.1	64.5	62.8	61.5	61.5	61.0	62.3
70°	59.3	57.1	54.1	51.4	49.7	49.7	47.5	47.1	47.1	47.1	46.6
72.5°	45.8	41.9	40.5	39.7	39.7	39.7	38.8	38.8	38.4	38.8	38.4
75°	34.0	33.6	32.7	32.3	32.3	31.8	31.4	31.4	31.4	31.4	31.4
77.5°	26.6	26.6	25.7	25.3	25.3	25.3	24.9	24.9	24.4	24.4	24.4
80°	19.6	19.6	18.7	18.7	18.7	18.3	18.3	18.3	18.7	18.3	18.3
82.5°	13.5	13.5	13.1	13.5	13.1	12.6	12.6	12.6	12.2	12.6	12.6
85°	7.8	7.8	7.4	7.0	7.4	7.4	7.0	7.4	7.0	7.4	7.0
87.5°	3.1	2.6	2.6	2.6	2.2	2.6	2.2	2.2	2.6	2.2	2.6
90°	18.3	18.9	19.6	20.3	20.6	20.8	21.1	21.4	21.7	22.0	21.7
92.5°	20.2	21.4	22.5	23.6	24.2	24.3	24.5	24.6	24.8	25.0	24.8
95°	23.9	25.1	26.2	27.3	27.9	27.9	27.9	27.9	27.9	27.9	27.9
97.5°	24.8	26.1	27.4	28.7	29.4	29.5	29.6	29.8	29.9	30.1	29.9
100°	25.5	26.8	28.1	29.4	30.1	30.2	30.3	30.5	30.6	30.8	30.6
102.5°	48.9	43.5	38.2	32.8	30.1	30.3	30.6	30.9	31.3	31.6	31.3
105°	131.9	103.0	74.1	45.2	30.8	31.0	31.3	31.6	32.0	32.3	32.0
107.5°	260.5	235.4	210.3	185.2	172.6	161.9	140.5	119.2	97.8	76.4	97.8
110°	325.8	320.4	315.0	309.6	306.9	295.2	271.9	248.6	225.2	201.9	225.2

TEST NUMBER: P1010913

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	378.9	380.3	381.8	383.3	384.0	383.8	383.5	383.2	382.9	382.6	382.9
115°	423.1	424.7	426.4	428.0	428.8	429.1	429.8	430.5	431.1	431.8	431.1
117.5°	466.1	467.4	468.7	470.0	470.7	470.8	470.9	471.1	471.2	471.4	471.2
120°	508.0	509.3	510.6	511.9	512.5	512.5	512.5	512.5	512.5	512.5	512.5
122.5°	549.3	550.1	551.0	551.8	552.2	552.3	552.4	552.6	552.7	552.9	552.7
125°	587.7	588.1	588.4	588.7	588.9	589.1	589.4	589.7	590.1	590.4	590.1
127.5°	626.8	627.3	627.8	628.3	628.5	628.3	628.0	627.7	627.4	627.1	627.4
130°	661.5	662.1	662.8	663.5	663.8	663.6	663.3	663.0	662.6	662.3	662.6
132.5°	694.5	695.2	695.8	696.5	696.8	696.6	696.1	695.6	695.1	694.6	695.1
135°	728.2	728.7	729.2	729.7	729.9	729.7	729.2	728.7	728.2	727.7	728.2
137.5°	757.8	758.6	759.5	760.3	760.7	760.5	760.2	759.9	759.5	759.2	759.5
140°	786.3	787.0	787.6	788.3	788.6	788.4	788.1	787.8	787.4	787.1	787.4
142.5°	813.3	813.8	814.3	814.8	815.0	814.8	814.3	813.8	813.3	812.8	813.3
145°	838.1	838.5	838.8	839.1	839.3	839.3	839.3	839.3	839.3	839.3	839.3
147.5°	860.9	861.2	861.5	861.8	862.0	861.6	860.8	860.0	859.2	858.4	859.2
150°	881.4	881.8	882.1	882.4	882.6	882.4	881.9	881.4	880.9	880.4	880.9
152.5°	899.4	900.1	900.7	901.4	901.7	901.3	900.5	899.6	898.8	898.0	898.8
155°	915.7	916.5	917.4	918.2	918.6	918.1	917.1	916.2	915.2	914.2	915.2
157.5°	930.6	931.6	932.5	933.5	934.0	933.3	932.0	930.7	929.4	928.1	929.4
160°	943.1	944.1	945.0	946.0	946.5	945.9	944.8	943.6	942.5	941.3	942.5
162.5°	954.2	955.4	956.5	957.6	958.2	957.7	956.7	955.8	954.8	953.8	954.8
165°	963.9	965.2	966.5	967.8	968.5	967.9	966.8	965.7	964.5	963.4	964.5
167.5°	972.0	973.3	974.6	975.9	976.6	975.9	974.6	973.3	972.0	970.7	972.0
170°	978.6	979.9	981.2	982.5	983.2	982.5	981.2	979.9	978.6	977.3	978.6
172.5°	983.0	984.3	985.6	986.9	987.6	986.9	985.4	983.9	982.5	981.0	982.5
175°	986.5	987.7	988.8	989.9	990.5	989.9	988.6	987.3	986.0	984.7	986.0
177.5°	988.2	989.5	990.8	992.1	992.7	991.9	990.3	988.6	987.0	985.4	987.0
180°	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3

TEST NUMBER: P1010913

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	549.8	547.2	545.4	544.1	542.8	546.7	541.5	535.8	531.9	529.3	528.4
5°	607.3	601.7	596.9	592.9	593.8	593.8	584.7	574.6	565.9	561.1	555.9
7.5°	674.0	667.9	658.3	656.2	654.4	643.5	634.4	616.0	605.1	594.2	584.7
10°	740.3	732.4	723.3	720.2	715.9	702.4	688.4	664.9	651.4	631.3	618.7
12.5°	802.2	792.6	783.5	781.3	774.7	763.0	739.0	714.6	691.5	670.1	647.9
15°	854.1	851.5	837.5	828.8	814.4	798.3	793.0	759.9	730.7	708.5	668.4
17.5°	897.7	885.5	872.4	866.7	861.1	842.3	823.6	789.6	758.2	725.5	699.7
20°	932.6	919.0	909.9	901.6	899.0	877.6	848.0	817.9	783.5	746.8	713.3
22.5°	934.3	932.6	926.5	921.7	916.4	902.5	878.9	841.4	804.8	764.7	720.7
25°	898.1	895.5	912.9	908.6	912.1	906.8	894.2	862.8	820.1	773.0	728.5
27.5°	789.1	815.7	843.2	852.8	859.3	878.1	884.2	866.7	832.3	782.1	732.4
30°	640.9	676.2	720.7	744.7	763.0	797.8	843.2	848.9	832.7	792.6	731.6
32.5°	503.1	535.4	571.1	599.5	623.9	695.4	756.4	800.5	808.3	787.4	733.8
35°	405.5	419.4	453.4	480.5	513.6	574.6	646.6	717.6	765.6	768.2	727.2
37.5°	334.4	341.8	371.5	386.7	406.3	460.0	527.1	620.0	694.5	729.8	708.9
40°	276.8	293.9	310.9	319.6	333.5	370.6	435.1	507.9	600.3	665.7	680.6
42.5°	240.2	247.6	258.5	270.7	279.5	311.7	354.9	421.6	504.9	596.0	637.0
45°	211.9	214.5	225.8	233.7	242.8	265.5	296.0	351.8	425.1	514.9	584.7
47.5°	188.3	193.6	199.7	204.5	210.6	228.0	254.2	294.7	359.2	439.5	514.5
50°	167.4	170.5	178.3	180.5	184.9	197.1	217.1	248.1	301.3	365.4	443.0
52.5°	147.8	153.5	156.5	159.6	163.5	173.5	186.6	211.9	252.0	312.2	378.0
55°	132.5	134.3	138.6	141.3	144.3	151.3	162.6	181.4	212.8	260.7	323.1
57.5°	117.7	117.7	122.1	124.3	127.3	132.5	142.6	157.0	179.6	215.4	272.5
60°	102.0	102.5	105.9	108.6	109.4	114.7	122.9	134.3	151.7	177.9	224.5
62.5°	88.1	90.2	92.0	92.9	95.9	99.0	105.9	113.8	126.0	149.1	182.2
65°	76.3	76.7	78.0	78.9	80.2	83.7	88.9	94.2	104.6	121.6	148.7
67.5°	62.8	64.5	66.3	66.3	67.6	69.3	74.6	78.9	86.8	96.8	115.1
70°	47.1	48.0	50.6	51.9	53.6	56.7	59.3	61.9	68.0	75.4	89.4
72.5°	39.2	39.2	40.1	40.5	40.5	42.7	46.6	49.3	52.3	57.5	67.1
75°	31.4	31.4	32.7	32.3	33.1	34.0	34.4	36.2	37.9	41.9	47.5
77.5°	24.9	25.3	25.3	25.7	25.7	26.2	26.6	27.5	28.3	30.5	33.1
80°	18.3	18.7	18.7	19.2	19.2	19.6	20.1	20.5	21.4	22.2	23.5
82.5°	12.6	13.1	13.1	13.5	13.1	13.5	14.0	14.0	14.4	15.3	15.7
85°	7.4	7.4	7.8	7.4	7.4	7.4	7.8	7.8	8.3	9.6	9.6
87.5°	2.2	2.6	2.2	2.6	2.6	2.6	2.6	3.1	3.1	3.5	3.9
90°	21.4	21.1	20.8	20.6	20.3	19.6	18.9	18.3	17.6	15.5	13.4
92.5°	24.6	24.5	24.3	24.2	23.6	22.5	21.4	20.2	19.1	17.6	16.2
95°	27.9	27.9	27.9	27.9	27.3	26.2	25.1	23.9	22.8	21.0	19.2
97.5°	29.8	29.6	29.5	29.4	28.7	27.4	26.1	24.8	23.5	31.8	40.1
100°	30.5	30.3	30.2	30.1	29.4	28.1	26.8	25.5	24.2	49.7	75.1
102.5°	30.9	30.6	30.3	30.1	32.8	38.2	43.5	48.9	54.3	82.7	111.1
105°	31.6	31.3	31.0	30.8	45.2	74.1	103.0	131.9	160.8	175.5	190.2
107.5°	119.2	140.5	161.9	172.6	185.2	210.3	235.4	260.5	285.6	283.2	280.7
110°	248.6	271.9	295.2	306.9	309.6	315.0	320.4	325.8	331.2	329.4	327.6

TEST NUMBER: P1010913

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	383.2	383.5	383.8	384.0	383.3	381.8	380.3	378.9	377.4	375.6	373.8
115°	430.5	429.8	429.1	428.8	428.0	426.4	424.7	423.1	421.5	420.0	418.6
117.5°	471.1	470.9	470.8	470.7	470.0	468.7	467.4	466.1	464.8	464.0	463.2
120°	512.5	512.5	512.5	512.5	511.9	510.6	509.3	508.0	506.7	506.2	505.7
122.5°	552.6	552.4	552.3	552.2	551.8	551.0	550.1	549.3	548.5	547.9	547.2
125°	589.7	589.4	589.1	588.9	588.7	588.4	588.1	587.7	587.4	586.8	586.1
127.5°	627.7	628.0	628.3	628.5	628.3	627.8	627.3	626.8	626.3	625.5	624.7
130°	663.0	663.3	663.6	663.8	663.5	662.8	662.1	661.5	660.8	660.2	659.5
132.5°	695.6	696.1	696.6	696.8	696.5	695.8	695.2	694.5	693.9	693.4	692.9
135°	728.7	729.2	729.7	729.9	729.7	729.2	728.7	728.2	727.7	727.0	726.4
137.5°	759.9	760.2	760.5	760.7	760.3	759.5	758.6	757.8	757.0	756.7	756.4
140°	787.8	788.1	788.4	788.6	788.3	787.6	787.0	786.3	785.7	785.2	784.7
142.5°	813.8	814.3	814.8	815.0	814.8	814.3	813.8	813.3	812.8	812.3	811.8
145°	839.3	839.3	839.3	839.3	839.1	838.8	838.5	838.1	837.8	837.5	837.1
147.5°	860.0	860.8	861.6	862.0	861.8	861.5	861.2	860.9	860.6	860.3	859.9
150°	881.4	881.9	882.4	882.6	882.4	882.1	881.8	881.4	881.1	880.8	880.5
152.5°	899.6	900.5	901.3	901.7	901.4	900.7	900.1	899.4	898.8	898.6	898.4
155°	916.2	917.1	918.1	918.6	918.2	917.4	916.5	915.7	914.9	914.7	914.6
157.5°	930.7	932.0	933.3	934.0	933.5	932.5	931.6	930.6	929.6	929.8	929.9
160°	943.6	944.8	945.9	946.5	946.0	945.0	944.1	943.1	942.1	942.3	942.4
162.5°	955.8	956.7	957.7	958.2	957.6	956.5	955.4	954.2	953.1	953.3	953.4
165°	965.7	966.8	967.9	968.5	967.8	966.5	965.2	963.9	962.6	962.8	963.0
167.5°	973.3	974.6	975.9	976.6	975.9	974.6	973.3	972.0	970.7	970.7	970.7
170°	979.9	981.2	982.5	983.2	982.5	981.2	979.9	978.6	977.3	977.3	977.3
172.5°	983.9	985.4	986.9	987.6	986.9	985.6	984.3	983.0	981.7	981.5	981.4
175°	987.3	988.6	989.9	990.5	989.9	988.8	987.7	986.5	985.4	985.2	985.1
177.5°	988.6	990.3	991.9	992.7	992.1	990.8	989.5	988.2	986.9	986.7	986.5
180°	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3

TEST NUMBER: P1010913

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	527.1	524.9	522.7	522.7	517.9	513.6	511.4	512.3	509.7	506.2	502.7
5°	550.2	541.5	539.7	534.9	528.4	519.3	514.5	510.1	504.9	497.9	491.4
7.5°	571.6	560.2	554.1	549.3	536.7	524.0	513.6	506.6	497.5	487.0	479.1
10°	599.5	578.5	572.0	561.1	543.2	525.4	513.1	501.8	489.2	477.0	466.5
12.5°	621.7	597.7	585.5	574.6	551.5	528.8	508.4	494.4	479.1	465.6	452.1
15°	647.0	620.0	598.6	585.5	556.3	528.8	505.7	486.1	469.1	452.5	440.8
17.5°	659.2	625.2	615.6	596.9	554.6	527.1	498.8	477.8	457.3	438.2	424.2
20°	678.4	638.7	614.7	602.1	564.6	524.0	490.9	466.9	445.6	425.1	410.3
22.5°	679.7	636.5	620.8	596.9	550.6	514.9	483.9	454.7	429.9	410.7	395.4
25°	676.6	632.6	610.8	591.6	553.3	509.7	470.0	441.2	416.8	394.6	376.7
27.5°	675.3	621.3	600.8	581.6	538.4	494.4	461.7	429.0	401.1	381.5	363.2
30°	673.6	609.1	584.2	562.0	522.3	482.6	443.4	415.1	388.5	363.6	345.3
32.5°	662.3	592.5	567.2	543.7	500.9	461.3	430.3	400.2	371.5	348.3	331.8
35°	658.8	577.2	544.1	518.8	477.0	441.6	409.0	384.1	357.1	334.0	314.3
37.5°	648.7	561.5	525.8	493.5	449.9	416.4	392.4	367.5	341.4	316.5	300.8
40°	631.3	543.2	502.7	469.6	424.6	390.6	368.4	350.1	324.4	302.1	283.0
42.5°	605.6	524.5	480.9	446.0	396.3	364.5	346.2	328.7	306.9	283.8	268.1
45°	575.9	499.6	459.1	420.3	369.7	338.8	319.6	309.1	289.1	269.4	251.1
47.5°	535.4	473.9	433.8	393.7	342.2	312.2	296.9	286.4	272.5	251.1	236.3
50°	484.4	440.8	402.8	367.1	315.2	286.4	271.2	263.3	251.6	236.3	221.9
52.5°	427.7	402.4	371.0	337.9	287.7	260.7	246.8	240.7	231.9	217.6	205.3
55°	370.6	359.7	338.3	305.6	259.0	236.7	224.5	216.7	210.1	199.7	189.2
57.5°	319.6	314.3	299.5	274.2	235.0	211.9	201.4	196.2	191.0	183.1	172.6
60°	266.8	272.5	257.2	244.6	208.8	188.8	179.6	174.0	171.3	164.4	157.8
62.5°	221.0	226.3	217.6	208.0	182.7	164.8	159.1	153.9	152.2	146.1	139.5
65°	179.6	186.2	179.6	174.4	159.1	144.3	137.3	134.7	133.0	129.1	123.8
67.5°	143.0	149.5	146.5	139.9	135.2	122.9	119.0	116.4	115.5	112.5	108.1
70°	107.7	116.8	117.7	113.8	109.4	103.8	101.1	100.3	98.1	95.5	92.9
72.5°	77.6	88.1	88.5	88.5	85.9	85.9	83.3	82.0	82.0	79.3	76.3
75°	57.1	64.1	65.0	65.8	67.1	68.4	66.7	66.7	66.3	63.7	62.3
77.5°	37.9	44.0	46.2	49.3	51.0	51.0	51.9	52.8	51.9	50.6	49.7
80°	24.4	28.8	31.4	33.1	35.8	37.1	38.4	38.8	37.9	37.5	36.2
82.5°	16.1	17.4	18.7	20.9	24.0	26.2	26.2	25.7	26.6	26.2	25.7
85°	9.2	10.0	10.5	10.9	12.6	14.8	15.3	15.7	16.6	15.7	14.8
87.5°	3.5	3.9	3.9	3.9	4.8	5.2	6.5	8.3	7.8	7.0	7.0
90°	11.3	9.2	8.1	7.3	5.6	4.0	2.3	0.7	2.3	4.0	5.6
92.5°	14.7	13.2	12.5	13.0	14.0	14.9	15.9	16.9	15.9	14.9	14.0
95°	17.4	15.6	14.7	18.0	24.7	31.4	38.1	44.8	38.1	31.4	24.7
97.5°	48.4	56.7	60.9	63.2	67.8	72.3	76.9	81.5	76.9	72.3	67.8
100°	100.6	126.1	138.8	137.2	133.9	130.6	127.4	124.1	127.4	130.6	133.9
102.5°	139.5	167.9	182.1	181.0	178.9	176.8	174.7	172.6	174.7	176.8	178.9
105°	204.9	219.6	226.9	226.0	224.2	222.4	220.6	218.8	220.6	222.4	224.2
107.5°	278.3	275.8	274.6	273.9	272.4	270.9	269.5	268.0	269.5	270.9	272.4
110°	325.8	324.0	323.1	322.4	321.1	319.8	318.5	317.2	318.5	319.8	321.1

TEST NUMBER: P1010913

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	372.0	370.2	369.3	368.7	367.6	366.5	365.3	364.2	365.3	366.5	367.6
115°	417.1	415.6	414.9	414.4	413.4	412.5	411.5	410.5	411.5	412.5	413.4
117.5°	462.3	461.5	461.1	460.5	459.4	458.3	457.1	456.0	457.1	458.3	459.4
120°	505.2	504.7	504.4	503.7	502.2	500.7	499.3	497.8	499.3	500.7	502.2
122.5°	546.6	545.9	545.6	545.0	543.9	542.7	541.6	540.4	541.6	542.7	543.9
125°	585.5	584.8	584.5	583.8	582.5	581.2	579.9	578.6	579.9	581.2	582.5
127.5°	623.9	623.1	622.7	622.0	620.7	619.4	618.1	616.8	618.1	619.4	620.7
130°	658.9	658.2	657.9	657.2	655.9	654.6	653.3	652.0	653.3	654.6	655.9
132.5°	692.4	691.9	691.7	691.0	689.7	688.4	687.1	685.8	687.1	688.4	689.7
135°	725.7	725.0	724.7	724.2	723.2	722.3	721.3	720.3	721.3	722.3	723.2
137.5°	756.1	755.8	755.6	754.9	753.6	752.3	751.0	749.7	751.0	752.3	753.6
140°	784.2	783.7	783.5	783.0	782.0	781.1	780.1	779.1	780.1	781.1	782.0
142.5°	811.3	810.8	810.6	810.1	809.1	808.2	807.2	806.2	807.2	808.2	809.1
145°	836.8	836.5	836.3	835.7	834.6	833.5	832.3	831.2	832.3	833.5	834.6
147.5°	859.6	859.3	859.1	858.7	857.9	857.0	856.2	855.4	856.2	857.0	857.9
150°	880.2	879.9	879.7	879.5	879.0	878.5	878.0	877.5	878.0	878.5	879.0
152.5°	898.3	898.1	898.0	897.9	897.8	897.6	897.5	897.3	897.5	897.6	897.8
155°	914.4	914.3	914.2	914.4	914.7	915.0	915.3	915.6	915.3	915.0	914.7
157.5°	930.1	930.2	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
160°	942.6	942.7	942.8	942.9	943.0	943.2	943.3	943.5	943.3	943.2	943.0
162.5°	953.6	953.7	953.8	954.0	954.5	955.0	955.5	956.0	955.5	955.0	954.5
165°	963.1	963.3	963.4	963.6	964.1	964.6	965.1	965.6	965.1	964.6	964.1
167.5°	970.7	970.7	970.7	971.0	971.7	972.4	973.0	973.7	973.0	972.4	971.7
170°	977.3	977.3	977.3	977.6	978.3	979.0	979.6	980.3	979.6	979.0	978.3
172.5°	981.2	981.1	981.0	981.4	982.2	983.1	983.9	984.7	983.9	983.1	982.2
175°	984.9	984.8	984.7	985.1	985.9	986.7	987.5	988.3	987.5	986.7	985.9
177.5°	986.4	986.2	986.1	986.5	987.3	988.2	989.0	989.8	989.0	988.2	987.3
180°	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3

TEST NUMBER: P1010913

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	502.7	500.5	499.6	497.5	492.2	488.7	484.8	482.2	482.6	480.5	481.8
5°	487.0	486.6	483.5	479.1	471.7	467.8	460.8	457.3	455.6	456.0	453.4
7.5°	473.9	470.0	467.8	460.8	453.9	445.6	439.9	436.9	434.2	431.6	429.9
10°	459.1	455.6	452.1	444.7	435.1	427.3	419.4	416.4	412.4	410.7	409.4
12.5°	443.4	441.2	436.9	428.1	417.2	409.8	400.7	398.9	393.7	390.2	389.3
15°	429.0	427.7	419.8	409.8	398.9	391.5	383.7	378.4	369.7	371.5	368.4
17.5°	413.7	408.1	403.3	389.8	384.5	373.2	364.0	361.4	355.3	351.4	347.5
20°	396.7	393.3	387.2	378.4	365.8	352.7	345.7	341.4	337.9	331.8	330.0
22.5°	380.6	376.3	371.0	359.7	348.8	337.9	328.3	324.4	320.0	315.7	313.0
25°	368.0	361.4	355.8	341.8	330.9	321.8	315.7	309.1	303.0	300.4	299.5
27.5°	348.3	344.4	338.8	325.7	315.7	305.6	300.0	295.6	289.1	286.0	283.4
30°	335.7	327.9	321.3	310.9	300.8	289.9	284.7	279.5	275.5	271.6	268.6
32.5°	318.7	312.6	307.4	296.9	286.9	276.8	271.2	263.3	261.2	258.1	254.6
35°	302.1	298.2	292.5	281.2	270.3	263.3	257.2	249.8	247.2	245.0	242.0
37.5°	286.4	280.8	276.8	265.9	256.4	248.1	243.3	237.2	235.4	232.8	230.6
40°	272.9	267.3	263.3	252.4	242.4	233.7	230.6	224.5	221.9	218.9	217.6
42.5°	257.7	252.9	247.6	239.8	229.3	220.6	214.5	211.0	207.5	206.2	203.6
45°	241.5	237.2	233.2	224.5	213.6	207.5	202.3	197.5	194.9	192.7	191.0
47.5°	227.6	223.7	218.4	208.8	200.1	194.4	189.2	184.4	181.8	179.2	177.0
50°	211.5	209.3	203.6	194.4	186.2	179.6	174.8	170.5	168.7	165.7	162.2
52.5°	197.1	193.1	188.3	180.9	173.5	165.7	159.1	156.5	153.5	151.7	148.7
55°	180.1	177.4	172.2	165.7	157.8	151.3	146.5	143.0	139.1	137.3	133.4
57.5°	165.7	160.9	158.3	150.0	142.6	136.0	132.5	129.1	124.7	122.1	120.3
60°	150.0	145.6	141.7	134.7	129.5	122.5	117.3	114.2	111.2	107.7	105.9
62.5°	134.7	131.2	126.4	120.8	114.2	108.6	104.6	100.3	98.5	95.0	93.7
65°	118.2	115.5	111.6	105.1	99.8	95.0	91.1	87.6	85.9	84.6	83.7
67.5°	103.3	99.8	97.2	91.6	85.9	82.0	79.8	77.6	75.4	74.1	72.8
70°	88.1	85.5	82.8	77.6	73.7	70.2	68.4	66.7	65.4	64.1	62.8
72.5°	72.4	71.1	68.4	65.0	61.9	59.3	58.0	55.8	54.5	52.3	51.4
75°	59.7	57.5	56.2	53.2	50.6	48.4	46.6	44.0	42.3	41.4	41.0
77.5°	47.1	46.2	44.5	41.9	40.5	38.4	35.8	34.9	34.0	34.0	33.6
80°	35.3	34.0	32.7	30.5	29.2	27.5	27.5	27.5	27.0	27.5	27.0
82.5°	24.0	23.1	22.2	20.9	20.5	20.5	20.9	20.9	20.9	20.9	20.9
85°	14.0	14.0	14.0	14.4	14.0	14.0	14.4	14.8	14.4	14.4	14.0
87.5°	6.5	6.5	7.0	7.0	7.4	7.4	7.4	7.4	7.4	7.4	7.8
90°	7.3	8.1	9.2	11.3	13.4	15.5	17.6	18.3	18.9	19.6	20.3
92.5°	13.0	12.5	13.2	14.7	16.2	17.6	19.1	20.2	21.4	22.5	23.6
95°	18.0	14.7	15.6	17.4	19.2	21.0	22.8	23.9	25.1	26.2	27.3
97.5°	63.2	60.9	56.7	48.4	40.1	31.8	23.5	24.8	26.1	27.4	28.7
100°	137.2	138.8	126.1	100.6	75.1	49.7	24.2	25.5	26.8	28.1	29.4
102.5°	181.0	182.1	167.9	139.5	111.1	82.7	54.3	48.9	43.5	38.2	32.8
105°	226.0	226.9	219.6	204.9	190.2	175.5	160.8	131.9	103.0	74.1	45.2
107.5°	273.9	274.6	275.8	278.3	280.7	283.2	285.6	260.5	235.4	210.3	185.2
110°	322.4	323.1	324.0	325.8	327.6	329.4	331.2	325.8	320.4	315.0	309.6

TEST NUMBER: P1010913

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	368.7	369.3	370.2	372.0	373.8	375.6	377.4	378.9	380.3	381.8	383.3
115°	414.4	414.9	415.6	417.1	418.6	420.0	421.5	423.1	424.7	426.4	428.0
117.5°	460.5	461.1	461.5	462.3	463.2	464.0	464.8	466.1	467.4	468.7	470.0
120°	503.7	504.4	504.7	505.2	505.7	506.2	506.7	508.0	509.3	510.6	511.9
122.5°	545.0	545.6	545.9	546.6	547.2	547.9	548.5	549.3	550.1	551.0	551.8
125°	583.8	584.5	584.8	585.5	586.1	586.8	587.4	587.7	588.1	588.4	588.7
127.5°	622.0	622.7	623.1	623.9	624.7	625.5	626.3	626.8	627.3	627.8	628.3
130°	657.2	657.9	658.2	658.9	659.5	660.2	660.8	661.5	662.1	662.8	663.5
132.5°	691.0	691.7	691.9	692.4	692.9	693.4	693.9	694.5	695.2	695.8	696.5
135°	724.2	724.7	725.0	725.7	726.4	727.0	727.7	728.2	728.7	729.2	729.7
137.5°	754.9	755.6	755.8	756.1	756.4	756.7	757.0	757.8	758.6	759.5	760.3
140°	783.0	783.5	783.7	784.2	784.7	785.2	785.7	786.3	787.0	787.6	788.3
142.5°	810.1	810.6	810.8	811.3	811.8	812.3	812.8	813.3	813.8	814.3	814.8
145°	835.7	836.3	836.5	836.8	837.1	837.5	837.8	838.1	838.5	838.8	839.1
147.5°	858.7	859.1	859.3	859.6	859.9	860.3	860.6	860.9	861.2	861.5	861.8
150°	879.5	879.7	879.9	880.2	880.5	880.8	881.1	881.4	881.8	882.1	882.4
152.5°	897.9	898.0	898.1	898.3	898.4	898.6	898.8	899.4	900.1	900.7	901.4
155°	914.4	914.2	914.3	914.4	914.6	914.7	914.9	915.7	916.5	917.4	918.2
157.5°	930.3	930.3	930.2	930.1	929.9	929.8	929.6	930.6	931.6	932.5	933.5
160°	942.9	942.8	942.7	942.6	942.4	942.3	942.1	943.1	944.1	945.0	946.0
162.5°	954.0	953.8	953.7	953.6	953.4	953.3	953.1	954.2	955.4	956.5	957.6
165°	963.6	963.4	963.3	963.1	963.0	962.8	962.6	963.9	965.2	966.5	967.8
167.5°	971.0	970.7	970.7	970.7	970.7	970.7	970.7	972.0	973.3	974.6	975.9
170°	977.6	977.3	977.3	977.3	977.3	977.3	977.3	978.6	979.9	981.2	982.5
172.5°	981.4	981.0	981.1	981.2	981.4	981.5	981.7	983.0	984.3	985.6	986.9
175°	985.1	984.7	984.8	984.9	985.1	985.2	985.4	986.5	987.7	988.8	989.9
177.5°	986.5	986.1	986.2	986.4	986.5	986.7	986.9	988.2	989.5	990.8	992.1
180°	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3

TEST NUMBER: P1010913

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	481.3	481.8	480.5	477.8	477.4	478.3	480.9	480.0	477.8	481.8	478.3
5°	454.7	452.5	451.7	452.5	449.9	448.6	451.2	449.9	451.2	451.7	453.0
7.5°	429.0	429.4	426.8	427.3	423.8	424.6	424.6	424.6	426.0	426.8	428.6
10°	406.8	407.6	404.6	405.0	402.4	400.7	402.0	404.6	404.6	404.6	405.5
12.5°	388.9	385.0	382.8	382.4	379.3	378.4	381.0	381.9	384.1	384.1	385.4
15°	366.7	365.8	364.0	364.0	356.6	358.4	359.2	362.3	366.7	363.2	364.0
17.5°	346.6	344.4	342.2	341.4	340.5	337.9	341.4	340.9	343.6	344.0	345.3
20°	328.7	327.0	322.6	323.1	323.9	320.0	322.2	322.2	324.8	327.4	330.5
22.5°	311.3	309.5	307.4	308.2	305.6	304.8	304.8	306.9	310.0	312.2	311.7
25°	297.8	294.7	293.4	292.1	290.8	291.7	290.4	292.5	294.7	296.0	294.7
27.5°	282.5	281.2	278.6	277.3	275.1	276.0	276.8	278.6	279.9	279.9	281.2
30°	267.7	265.9	265.1	263.8	263.8	262.0	262.5	264.2	265.5	266.8	268.6
32.5°	253.3	252.0	250.7	250.7	249.8	249.4	248.9	251.6	251.6	254.2	254.2
35°	241.5	239.4	239.4	237.2	238.0	237.6	236.7	238.5	238.9	240.7	240.2
37.5°	228.5	228.5	227.6	225.4	223.7	224.1	226.3	226.3	227.6	227.1	228.5
40°	215.4	214.5	214.5	213.2	212.8	212.3	212.8	213.2	215.4	214.9	215.4
42.5°	202.3	202.7	200.6	200.6	200.6	199.2	199.7	200.1	201.0	201.9	203.2
45°	189.7	188.8	188.3	187.5	186.6	187.0	186.6	188.3	187.9	188.8	190.1
47.5°	176.1	174.8	174.4	172.6	172.6	173.5	173.1	174.4	174.8	176.1	175.3
50°	163.1	161.3	160.0	160.4	157.8	158.7	158.7	160.0	161.3	161.7	162.6
52.5°	147.8	147.4	146.9	144.7	144.3	143.9	144.3	144.7	146.5	147.8	148.2
55°	133.0	132.5	129.9	129.1	127.7	127.7	128.6	129.1	132.1	132.5	134.3
57.5°	119.5	118.2	115.1	114.7	114.7	114.7	113.4	115.1	116.0	118.2	118.2
60°	104.6	104.6	102.0	102.0	102.5	102.0	102.0	102.5	102.5	104.2	105.1
62.5°	92.9	92.4	92.4	91.6	91.1	91.6	91.1	91.1	91.6	92.9	94.2
65°	82.4	82.0	81.5	81.1	80.2	80.2	80.7	81.5	81.5	82.4	82.8
67.5°	72.4	72.4	71.5	71.5	71.1	70.6	71.1	70.6	72.4	72.4	72.8
70°	62.3	61.9	60.6	60.2	58.9	59.3	59.3	60.6	61.0	61.9	62.8
72.5°	50.1	50.1	49.3	48.4	48.8	48.0	48.0	48.4	48.4	49.7	50.1
75°	41.4	40.5	40.1	40.5	40.1	41.0	40.1	40.1	41.0	41.0	41.0
77.5°	34.0	34.0	33.6	33.6	34.0	33.6	34.0	34.0	34.0	33.6	34.0
80°	27.9	27.5	27.5	27.5	27.0	27.0	27.0	27.0	27.0	27.0	27.0
82.5°	20.9	20.9	20.5	20.9	20.9	20.5	20.9	20.5	20.5	20.9	20.9
85°	14.0	14.8	14.0	14.0	14.4	14.4	14.8	14.4	14.8	14.0	14.4
87.5°	7.4	7.8	7.8	7.4	7.4	7.8	7.8	7.8	8.3	7.4	7.8
90°	20.6	20.8	21.1	21.4	21.7	22.0	21.7	21.4	21.1	20.8	20.6
92.5°	24.2	24.3	24.5	24.6	24.8	25.0	24.8	24.6	24.5	24.3	24.2
95°	27.9	27.9	27.9	27.9	27.9	27.9	27.9	27.9	27.9	27.9	27.9
97.5°	29.4	29.5	29.6	29.8	29.9	30.1	29.9	29.8	29.6	29.5	29.4
100°	30.1	30.2	30.3	30.5	30.6	30.8	30.6	30.5	30.3	30.2	30.1
102.5°	30.1	30.3	30.6	30.9	31.3	31.6	31.3	30.9	30.6	30.3	30.1
105°	30.8	31.0	31.3	31.6	32.0	32.3	32.0	31.6	31.3	31.0	30.8
107.5°	172.6	161.9	140.5	119.2	97.8	76.4	97.8	119.2	140.5	161.9	172.6
110°	306.9	295.2	271.9	248.6	225.2	201.9	225.2	248.6	271.9	295.2	306.9

TEST NUMBER: P1010913

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	384.0	383.8	383.5	383.2	382.9	382.6	382.9	383.2	383.5	383.8	384.0
115°	428.8	429.1	429.8	430.5	431.1	431.8	431.1	430.5	429.8	429.1	428.8
117.5°	470.7	470.8	470.9	471.1	471.2	471.4	471.2	471.1	470.9	470.8	470.7
120°	512.5	512.5	512.5	512.5	512.5	512.5	512.5	512.5	512.5	512.5	512.5
122.5°	552.2	552.3	552.4	552.6	552.7	552.9	552.7	552.6	552.4	552.3	552.2
125°	588.9	589.1	589.4	589.7	590.1	590.4	590.1	589.7	589.4	589.1	588.9
127.5°	628.5	628.3	628.0	627.7	627.4	627.1	627.4	627.7	628.0	628.3	628.5
130°	663.8	663.6	663.3	663.0	662.6	662.3	662.6	663.0	663.3	663.6	663.8
132.5°	696.8	696.6	696.1	695.6	695.1	694.6	695.1	695.6	696.1	696.6	696.8
135°	729.9	729.7	729.2	728.7	728.2	727.7	728.2	728.7	729.2	729.7	729.9
137.5°	760.7	760.5	760.2	759.9	759.5	759.2	759.5	759.9	760.2	760.5	760.7
140°	788.6	788.4	788.1	787.8	787.4	787.1	787.4	787.8	788.1	788.4	788.6
142.5°	815.0	814.8	814.3	813.8	813.3	812.8	813.3	813.8	814.3	814.8	815.0
145°	839.3	839.3	839.3	839.3	839.3	839.3	839.3	839.3	839.3	839.3	839.3
147.5°	862.0	861.6	860.8	860.0	859.2	858.4	859.2	860.0	860.8	861.6	862.0
150°	882.6	882.4	881.9	881.4	880.9	880.4	880.9	881.4	881.9	882.4	882.6
152.5°	901.7	901.3	900.5	899.6	898.8	898.0	898.8	899.6	900.5	901.3	901.7
155°	918.6	918.1	917.1	916.2	915.2	914.2	915.2	916.2	917.1	918.1	918.6
157.5°	934.0	933.3	932.0	930.7	929.4	928.1	929.4	930.7	932.0	933.3	934.0
160°	946.5	945.9	944.8	943.6	942.5	941.3	942.5	943.6	944.8	945.9	946.5
162.5°	958.2	957.7	956.7	955.8	954.8	953.8	954.8	955.8	956.7	957.7	958.2
165°	968.5	967.9	966.8	965.7	964.5	963.4	964.5	965.7	966.8	967.9	968.5
167.5°	976.6	975.9	974.6	973.3	972.0	970.7	972.0	973.3	974.6	975.9	976.6
170°	983.2	982.5	981.2	979.9	978.6	977.3	978.6	979.9	981.2	982.5	983.2
172.5°	987.6	986.9	985.4	983.9	982.5	981.0	982.5	983.9	985.4	986.9	987.6
175°	990.5	989.9	988.6	987.3	986.0	984.7	986.0	987.3	988.6	989.9	990.5
177.5°	992.7	991.9	990.3	988.6	987.0	985.4	987.0	988.6	990.3	991.9	992.7
180°	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3

TEST NUMBER: P1010913

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	481.8	483.5	481.8	478.3	481.8	483.9	486.1	489.6	491.4	491.4	494.0
5°	454.3	457.8	456.5	455.6	459.1	461.3	464.8	469.1	473.9	477.0	480.5
7.5°	429.9	432.1	434.2	434.2	437.7	442.5	447.8	453.0	459.1	463.4	466.1
10°	408.5	410.3	411.6	413.3	418.5	423.8	430.7	437.3	442.5	447.3	451.7
12.5°	388.0	390.6	393.7	395.0	398.9	405.5	412.0	419.8	428.1	432.9	437.3
15°	368.4	369.7	373.2	377.1	380.6	387.6	395.9	404.2	411.1	418.5	422.5
17.5°	348.3	348.8	357.9	355.8	367.1	373.6	378.0	385.8	397.2	403.3	409.4
20°	328.7	333.1	337.0	339.2	345.3	352.7	365.4	371.5	380.6	386.3	391.5
22.5°	313.5	320.0	320.0	325.2	328.3	335.3	344.4	356.2	366.2	370.1	377.6
25°	300.0	303.0	308.2	310.0	315.7	321.8	327.9	340.5	351.4	356.6	361.9
27.5°	282.5	286.4	293.4	293.4	300.8	307.4	314.8	323.1	334.0	341.4	347.0
30°	269.0	272.9	276.0	280.8	283.8	289.9	303.0	309.1	318.7	325.2	332.2
32.5°	256.4	259.4	262.0	267.3	270.7	277.7	284.7	295.6	303.9	310.0	317.4
35°	242.4	245.5	248.9	252.9	258.1	264.6	271.2	280.3	288.6	294.3	300.4
37.5°	229.3	231.5	236.7	239.4	243.7	249.8	258.1	267.7	275.1	279.5	285.6
40°	216.7	218.4	222.4	227.1	230.2	235.0	243.7	252.0	261.2	266.4	271.2
42.5°	203.2	205.3	208.8	213.6	218.4	223.7	228.5	238.0	246.3	250.7	255.9
45°	191.4	192.7	195.3	200.1	204.9	208.8	216.2	225.0	232.8	236.3	242.0
47.5°	177.4	178.8	182.7	184.9	190.1	195.3	202.7	211.5	218.4	221.9	227.1
50°	163.1	164.4	167.0	171.8	175.3	180.9	187.5	194.9	203.6	208.4	211.5
52.5°	149.1	151.7	153.9	157.8	162.2	167.9	174.0	180.9	188.3	193.1	196.6
55°	135.2	137.3	139.9	142.1	147.4	152.6	159.6	166.1	172.6	177.0	180.9
57.5°	119.5	122.5	125.1	129.5	133.4	137.8	145.6	150.8	158.7	161.7	165.2
60°	105.9	109.0	111.2	114.7	118.2	123.8	129.1	135.6	142.1	146.1	150.4
62.5°	94.6	95.9	97.2	100.7	104.2	109.4	114.7	121.2	128.2	130.4	133.8
65°	83.3	84.6	86.8	89.8	92.4	95.5	101.1	106.4	112.9	116.4	117.7
67.5°	73.7	75.0	75.4	77.6	79.8	83.3	86.3	91.6	97.7	99.8	102.5
70°	62.8	65.0	65.4	67.1	68.0	70.2	73.7	77.6	82.4	86.3	88.5
72.5°	50.1	53.2	54.1	56.7	58.0	60.2	62.8	65.8	68.9	70.6	72.4
75°	41.0	41.9	42.3	44.5	46.6	49.7	51.0	52.8	55.4	57.5	59.3
77.5°	34.0	34.4	34.9	34.9	35.3	37.1	39.7	41.9	43.6	44.5	45.8
80°	27.5	27.0	27.0	27.5	27.5	27.5	28.3	31.4	32.3	34.4	34.0
82.5°	21.4	20.5	20.9	20.5	20.5	20.5	20.5	20.9	20.9	22.2	23.1
85°	14.0	14.4	14.0	14.0	13.5	14.0	13.5	13.5	13.1	13.1	12.6
87.5°	7.4	7.8	7.4	7.4	7.0	7.4	7.0	7.0	6.5	6.5	5.7
90°	20.3	19.6	18.9	18.3	17.6	15.5	13.4	11.3	9.2	8.1	7.3
92.5°	23.6	22.5	21.4	20.2	19.1	17.6	16.2	14.7	13.2	12.5	13.0
95°	27.3	26.2	25.1	23.9	22.8	21.0	19.2	17.4	15.6	14.7	18.0
97.5°	28.7	27.4	26.1	24.8	23.5	31.8	40.1	48.4	56.7	60.9	63.2
100°	29.4	28.1	26.8	25.5	24.2	49.7	75.1	100.6	126.1	138.8	137.2
102.5°	32.8	38.2	43.5	48.9	54.3	82.7	111.1	139.5	167.9	182.1	181.0
105°	45.2	74.1	103.0	131.9	160.8	175.5	190.2	204.9	219.6	226.9	226.0
107.5°	185.2	210.3	235.4	260.5	285.6	283.2	280.7	278.3	275.8	274.6	273.9
110°	309.6	315.0	320.4	325.8	331.2	329.4	327.6	325.8	324.0	323.1	322.4

TEST NUMBER: P1010913

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	383.3	381.8	380.3	378.9	377.4	375.6	373.8	372.0	370.2	369.3	368.7
115°	428.0	426.4	424.7	423.1	421.5	420.0	418.6	417.1	415.6	414.9	414.4
117.5°	470.0	468.7	467.4	466.1	464.8	464.0	463.2	462.3	461.5	461.1	460.5
120°	511.9	510.6	509.3	508.0	506.7	506.2	505.7	505.2	504.7	504.4	503.7
122.5°	551.8	551.0	550.1	549.3	548.5	547.9	547.2	546.6	545.9	545.6	545.0
125°	588.7	588.4	588.1	587.7	587.4	586.8	586.1	585.5	584.8	584.5	583.8
127.5°	628.3	627.8	627.3	626.8	626.3	625.5	624.7	623.9	623.1	622.7	622.0
130°	663.5	662.8	662.1	661.5	660.8	660.2	659.5	658.9	658.2	657.9	657.2
132.5°	696.5	695.8	695.2	694.5	693.9	693.4	692.9	692.4	691.9	691.7	691.0
135°	729.7	729.2	728.7	728.2	727.7	727.0	726.4	725.7	725.0	724.7	724.2
137.5°	760.3	759.5	758.6	757.8	757.0	756.7	756.4	756.1	755.8	755.6	754.9
140°	788.3	787.6	787.0	786.3	785.7	785.2	784.7	784.2	783.7	783.5	783.0
142.5°	814.8	814.3	813.8	813.3	812.8	812.3	811.8	811.3	810.8	810.6	810.1
145°	839.1	838.8	838.5	838.1	837.8	837.5	837.1	836.8	836.5	836.3	835.7
147.5°	861.8	861.5	861.2	860.9	860.6	860.3	859.9	859.6	859.3	859.1	858.7
150°	882.4	882.1	881.8	881.4	881.1	880.8	880.5	880.2	879.9	879.7	879.5
152.5°	901.4	900.7	900.1	899.4	898.8	898.6	898.4	898.3	898.1	898.0	897.9
155°	918.2	917.4	916.5	915.7	914.9	914.7	914.6	914.4	914.3	914.2	914.4
157.5°	933.5	932.5	931.6	930.6	929.6	929.8	929.9	930.1	930.2	930.3	930.3
160°	946.0	945.0	944.1	943.1	942.1	942.3	942.4	942.6	942.7	942.8	942.9
162.5°	957.6	956.5	955.4	954.2	953.1	953.3	953.4	953.6	953.7	953.8	954.0
165°	967.8	966.5	965.2	963.9	962.6	962.8	963.0	963.1	963.3	963.4	963.6
167.5°	975.9	974.6	973.3	972.0	970.7	970.7	970.7	970.7	970.7	970.7	971.0
170°	982.5	981.2	979.9	978.6	977.3	977.3	977.3	977.3	977.3	977.3	977.6
172.5°	986.9	985.6	984.3	983.0	981.7	981.5	981.4	981.2	981.1	981.0	981.4
175°	989.9	988.8	987.7	986.5	985.4	985.2	985.1	984.9	984.8	984.7	985.1
177.5°	992.1	990.8	989.5	988.2	986.9	986.7	986.5	986.4	986.2	986.1	986.5
180°	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3	988.3

TEST NUMBER: P1010913

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	509.2	509.2	509.2	509.2
2.5°	496.1	499.2	505.3	510.5
5°	485.7	490.5	499.6	508.8
7.5°	473.0	480.5	492.2	504.9
10°	460.8	470.4	484.8	499.6
12.5°	448.6	458.7	473.9	493.1
15°	434.2	444.7	463.0	486.1
17.5°	421.6	435.5	452.1	475.2
20°	408.1	418.5	439.9	464.3
22.5°	391.1	408.5	428.6	454.3
25°	377.6	392.8	412.9	442.1
27.5°	361.0	378.9	403.3	429.0
30°	347.5	362.3	385.0	415.9
32.5°	331.8	349.2	372.8	403.3
35°	317.8	332.7	354.9	385.8
37.5°	301.3	317.4	342.2	369.7
40°	286.9	302.6	326.1	351.8
42.5°	269.4	286.0	309.5	331.3
45°	255.5	270.7	289.5	309.5
47.5°	238.5	254.6	272.9	286.9
50°	223.2	238.0	252.4	264.2
52.5°	206.7	220.2	233.2	242.0
55°	191.4	201.9	212.3	218.4
57.5°	173.5	183.5	192.3	195.8
60°	157.8	166.1	171.8	175.7
62.5°	141.3	147.4	151.7	153.9
65°	125.1	129.5	131.7	133.8
67.5°	108.6	112.5	113.8	116.4
70°	91.1	95.5	96.4	97.7
72.5°	78.0	78.0	79.8	81.5
75°	62.3	63.2	64.1	64.1
77.5°	48.8	48.8	49.7	50.1
80°	35.8	36.2	36.2	35.8
82.5°	24.4	25.3	24.4	24.0
85°	13.5	15.3	14.4	14.4
87.5°	5.7	5.7	6.5	5.7
90°	5.6	4.0	2.3	0.7
92.5°	14.0	14.9	15.9	16.9
95°	24.7	31.4	38.1	44.8
97.5°	67.8	72.3	76.9	81.5
100°	133.9	130.6	127.4	124.1
102.5°	178.9	176.8	174.7	172.6
105°	224.2	222.4	220.6	218.8
107.5°	272.4	270.9	269.5	268.0
110°	321.1	319.8	318.5	317.2

TEST NUMBER: P1010913

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	367.6	366.5	365.3	364.2
115°	413.4	412.5	411.5	410.5
117.5°	459.4	458.3	457.1	456.0
120°	502.2	500.7	499.3	497.8
122.5°	543.9	542.7	541.6	540.4
125°	582.5	581.2	579.9	578.6
127.5°	620.7	619.4	618.1	616.8
130°	655.9	654.6	653.3	652.0
132.5°	689.7	688.4	687.1	685.8
135°	723.2	722.3	721.3	720.3
137.5°	753.6	752.3	751.0	749.7
140°	782.0	781.1	780.1	779.1
142.5°	809.1	808.2	807.2	806.2
145°	834.6	833.5	832.3	831.2
147.5°	857.9	857.0	856.2	855.4
150°	879.0	878.5	878.0	877.5
152.5°	897.8	897.6	897.5	897.3
155°	914.7	915.0	915.3	915.6
157.5°	930.3	930.3	930.3	930.3
160°	943.0	943.2	943.3	943.5
162.5°	954.5	955.0	955.5	956.0
165°	964.1	964.6	965.1	965.6
167.5°	971.7	972.4	973.0	973.7
170°	978.3	979.0	979.6	980.3
172.5°	982.2	983.1	983.9	984.7
175°	985.9	986.7	987.5	988.3
177.5°	987.3	988.2	989.0	989.8
180°	988.3	988.3	988.3	988.3

(END OF REPORT)