

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010919

Luminaire Tested: S123RDIP-B560D1025UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010919
REPORT IS A COMBINATION OF REPORTS P993325 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D1025UB2750-4F0-XX-W2A-A_2700K
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6223.0 lumens
Efficiency: N/A
Efficacy: 118.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010919

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1010919

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43			35
1	95	91	87	84	86	82	79	77	66	64	62	52	50	49	38	38	37			31
2	87	80	74	69	78	72	68	63	59	55	52	46	44	42	34	33	32			26
3	79	70	64	58	72	64	58	53	52	48	44	41	38	36	31	29	27			23
4	73	63	55	49	66	57	51	46	46	42	38	37	34	31	28	26	24			20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21			18
6	62	50	42	37	56	46	39	34	38	33	29	30	26	24	23	21	19			16
7	57	45	38	32	51	41	35	30	34	29	26	27	24	21	21	19	17			14
8	53	41	34	29	48	38	31	27	31	26	23	25	21	19	19	17	15			13
9	49	37	30	25	45	34	28	24	29	24	20	23	20	17	18	15	14			11
10	46	34	27	23	42	32	25	21	26	22	18	21	18	15	17	14	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9510	9510	9510	9510
5°	9518	10953	9542	8126
10°	9434	13222	9475	7098
15°	9336	15006	9336	6258
20°	9145	16186	9196	5551
25°	9004	15378	8987	5066
30°	8841	10655	8823	4590
35°	8645	6841	8606	4232
40°	8401	4831	8359	3876
45°	7977	3865	7965	3528
50°	7454	3234	7430	3122
55°	6867	2665	6811	2647
60°	6289	2203	6227	2251
65°	5613	1763	5649	1908
70°	4989	1225	5124	1543
75°	4230	909	4401	1186
80°	3366	603	3654	889
85°	2401	286	2613	554

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 12696 cd/sqm

TEST NUMBER: P1010919

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.8	1.4
10°-20°	271.6	4.4
20°-30°	427.8	6.9
30°-40°	444.8	7.1
40°-50°	380.6	6.1
50°-60°	290.1	4.7
60°-70°	185.9	3.0
70°-80°	89.1	1.4
80°-90°	26.1	0.4
90°-100°	46.5	0.7
100°-110°	224.8	3.6
110°-120°	551.0	8.9
120°-130°	699.5	11.2
130°-140°	747.2	12.0
140°-150°	698.7	11.2
150°-160°	563.6	9.1
160°-170°	363.7	5.8
170°-180°	125.3	2.0
0°-30°	786.1	12.6
0°-40°	1231.0	19.8
0°-60°	1901.6	30.6
0°-90°	2202.6	35.4
90°-120°	822.3	13.2
90°-150°	2967.7	47.7
90°-180°	4020.0	64.6
0°-180°	6223.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	884	884	884	884	884	
5°	883	1049	885	778	883	84
15°	843	1491	843	622	843	237
25°	767	1536	766	506	767	353
35°	669	666	666	412	669	419
45°	537	356	536	324	537	414
55°	379	223	376	222	379	340
65°	232	129	234	139	232	232
75°	111	54	116	71	111	120
85°	25	13	27	25	25	28
90°	1	29	1	29	1	5
95°	60	37	60	37	60	71
105°	292	43	292	43	292	310
115°	548	576	548	576	548	541
125°	772	788	772	788	772	690
135°	961	971	961	971	961	740
145°	1109	1120	1109	1120	1109	694
155°	1222	1220	1222	1220	1222	563
165°	1288	1286	1288	1286	1288	364
175°	1319	1314	1319	1314	1319	126
180°	1319	1319	1319	1319	1319	

TEST NUMBER: P1010919

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	885.8	891.8	896.4	899.4	907.0	911.5	915.3	922.1	922.1	923.6	926.6
5°	882.8	895.6	904.7	916.8	932.7	940.2	950.8	959.9	972.8	979.6	986.4
7.5°	876.0	894.1	913.0	931.2	954.6	969.7	980.3	1003.8	1020.4	1040.9	1056.7
10°	866.9	891.8	916.0	944.0	975.8	998.5	1014.4	1045.4	1077.2	1105.9	1130.1
12.5°	855.5	885.8	920.6	954.6	999.2	1021.9	1047.7	1086.2	1131.6	1167.9	1200.5
15°	843.4	878.2	917.6	959.2	1015.1	1046.9	1084.0	1130.9	1181.5	1233.7	1278.4
17.5°	824.5	868.4	912.3	972.8	1038.6	1057.5	1089.3	1153.6	1216.3	1263.2	1317.7
20°	805.6	854.8	910.0	964.5	1035.6	1079.4	1108.9	1177.0	1244.3	1301.1	1353.3
22.5°	788.2	839.6	897.1	966.0	1032.5	1076.4	1113.5	1184.6	1262.5	1326.0	1390.3
25°	767.0	823.0	886.5	951.6	1032.5	1065.8	1106.7	1189.1	1271.6	1344.9	1424.4
27.5°	744.3	801.1	863.8	930.4	1004.5	1053.7	1093.8	1182.3	1282.9	1361.6	1443.3
30°	721.6	779.9	840.4	900.2	983.4	1030.3	1076.4	1174.0	1289.0	1379.0	1441.8
32.5°	699.7	748.9	808.6	866.9	949.3	1000.8	1053.0	1165.7	1291.2	1366.9	1397.1
35°	669.4	720.9	769.3	831.3	914.5	965.2	1026.5	1164.9	1281.4	1328.3	1313.2
37.5°	641.5	684.6	730.7	785.9	871.4	937.2	1000.8	1145.2	1248.9	1251.9	1166.4
40°	610.4	646.0	684.6	742.8	835.1	900.2	969.0	1115.0	1189.9	1145.2	994.7
42.5°	574.9	606.7	636.9	693.6	794.3	866.9	941.0	1077.2	1104.4	1001.5	844.9
45°	537.1	562.8	590.8	650.5	751.1	823.0	897.1	1018.9	990.9	845.7	696.7
47.5°	497.7	519.7	546.9	601.4	705.0	778.4	848.7	935.7	864.6	708.8	584.0
50°	458.4	475.8	502.3	558.2	658.1	724.7	789.7	846.4	746.6	608.2	482.6
52.5°	419.8	433.4	460.7	508.3	605.1	668.7	715.6	737.5	636.2	502.3	419.1
55°	379.0	394.1	412.3	460.7	556.7	603.6	634.6	633.9	529.5	425.9	346.4
57.5°	339.6	353.3	369.1	417.6	495.5	527.2	553.7	540.9	441.8	348.7	297.3
60°	304.8	312.4	329.8	370.7	429.7	456.9	472.0	450.1	360.8	294.3	245.8
62.5°	267.0	274.6	289.0	327.5	363.8	378.2	391.1	363.1	298.0	239.8	210.3
65°	232.2	242.1	251.1	282.1	301.8	319.2	317.7	294.3	233.0	195.2	171.0
67.5°	202.0	205.7	213.3	232.2	241.3	254.2	254.9	228.4	187.6	158.9	144.5
70°	169.4	173.2	178.5	187.6	193.6	196.7	195.2	171.7	141.5	124.1	111.2
72.5°	141.5	140.7	144.5	144.5	150.5	149.8	145.2	127.1	107.4	93.0	85.5
75°	111.2	112.0	112.7	111.2	108.9	105.9	102.1	88.5	75.6	68.8	62.0
77.5°	87.0	85.5	86.2	80.9	77.9	74.9	69.6	62.8	52.2	50.7	47.7
80°	62.0	61.3	60.5	58.2	51.4	48.4	44.6	40.8	38.6	37.1	36.3
82.5°	41.6	41.6	40.1	35.6	31.8	29.5	28.7	27.2	25.0	25.0	24.2
85°	25.0	24.2	22.7	18.2	15.9	15.9	15.9	15.9	14.4	14.4	13.6
87.5°	9.8	9.1	6.8	6.8	6.1	6.1	6.1	5.3	5.3	4.5	4.5
90°	1.0	3.2	5.4	7.5	9.7	10.8	12.2	15.0	17.9	20.7	23.5
92.5°	22.5	21.2	19.9	18.6	17.3	16.7	17.7	19.6	21.6	23.5	25.5
95°	59.8	50.9	41.9	33.0	24.1	19.6	20.8	23.2	25.6	28.0	30.4
97.5°	108.8	102.7	96.6	90.5	84.4	81.3	75.8	64.7	53.6	42.5	31.4
100°	165.6	170.0	174.3	178.7	183.0	185.2	168.2	134.2	100.3	66.3	32.3
102.5°	230.2	233.0	235.9	238.7	241.6	243.0	224.1	186.2	148.3	110.4	72.5
105°	292.0	294.4	296.8	299.1	301.5	302.7	292.9	273.3	253.8	234.2	214.6
107.5°	357.6	359.6	361.5	363.5	365.4	366.4	368.0	371.3	374.6	377.8	381.1
110°	423.3	425.0	426.8	428.5	430.2	431.1	432.3	434.7	437.1	439.5	441.9

TEST NUMBER: P1010919

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	486.0	487.5	489.0	490.5	492.0	492.8	494.0	496.4	498.8	501.2	503.6
115°	547.7	549.0	550.3	551.6	552.9	553.6	554.6	556.5	558.5	560.4	562.4
117.5°	608.4	609.9	611.5	613.0	614.5	615.3	615.8	616.9	618.0	619.1	620.2
120°	664.3	666.3	668.2	670.2	672.1	673.1	673.4	674.1	674.7	675.4	676.0
122.5°	721.1	722.6	724.2	725.7	727.2	728.0	728.4	729.3	730.2	731.0	731.9
125°	772.1	773.8	775.6	777.3	779.0	779.9	780.3	781.2	782.1	782.9	783.8
127.5°	823.0	824.7	826.5	828.2	829.9	830.8	831.3	832.4	833.5	834.6	835.7
130°	870.0	871.8	873.5	875.3	877.0	877.9	878.3	879.2	880.1	880.9	881.8
132.5°	915.1	916.8	918.6	920.3	922.0	922.9	923.2	923.9	924.6	925.2	925.9
135°	961.2	962.5	963.8	965.1	966.4	967.0	967.4	968.3	969.2	970.0	970.9
137.5°	1000.3	1002.1	1003.8	1005.6	1007.3	1008.2	1008.4	1008.8	1009.3	1009.7	1010.1
140°	1039.5	1040.8	1042.1	1043.4	1044.7	1045.4	1045.7	1046.4	1047.0	1047.7	1048.3
142.5°	1075.8	1077.1	1078.4	1079.7	1081.0	1081.7	1082.0	1082.7	1083.3	1084.0	1084.6
145°	1109.1	1110.6	1112.2	1113.7	1115.2	1116.0	1116.2	1116.6	1117.1	1117.5	1117.9
147.5°	1141.4	1142.5	1143.6	1144.7	1145.8	1146.3	1146.5	1147.0	1147.4	1147.9	1148.3
150°	1170.8	1171.5	1172.1	1172.8	1173.5	1173.8	1174.0	1174.4	1174.9	1175.3	1175.7
152.5°	1197.3	1197.5	1197.7	1198.0	1198.2	1198.3	1198.4	1198.6	1198.8	1199.0	1199.2
155°	1221.8	1221.4	1220.9	1220.5	1220.0	1219.8	1219.9	1220.1	1220.4	1220.6	1220.8
157.5°	1241.4	1241.4	1241.4	1241.4	1241.4	1241.4	1241.3	1241.1	1240.8	1240.6	1240.4
160°	1259.0	1258.8	1258.6	1258.3	1258.1	1258.0	1257.9	1257.7	1257.4	1257.2	1257.0
162.5°	1275.7	1275.0	1274.4	1273.7	1273.0	1272.7	1272.6	1272.4	1272.1	1271.9	1271.7
165°	1288.4	1287.8	1287.1	1286.5	1285.8	1285.5	1285.4	1285.2	1284.9	1284.7	1284.5
167.5°	1299.2	1298.3	1297.5	1296.6	1295.7	1295.3	1295.3	1295.3	1295.3	1295.3	1295.3
170°	1308.0	1307.1	1306.3	1305.4	1304.5	1304.1	1304.1	1304.1	1304.1	1304.1	1304.1
172.5°	1313.9	1312.8	1311.7	1310.6	1309.5	1309.0	1309.1	1309.3	1309.5	1309.7	1309.9
175°	1318.8	1317.7	1316.6	1315.5	1314.4	1313.9	1314.0	1314.2	1314.4	1314.6	1314.8
177.5°	1320.7	1319.6	1318.5	1317.4	1316.3	1315.8	1315.9	1316.1	1316.4	1316.6	1316.8
180°	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8

TEST NUMBER: P1010919

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	932.7	932.7	939.5	946.3	942.5	944.8	953.1	950.1	956.1	955.4	957.6
5°	1003.0	1011.4	1018.2	1032.5	1034.8	1032.5	1046.9	1050.7	1057.5	1049.2	1053.0
7.5°	1082.5	1099.9	1116.5	1137.7	1144.5	1146.0	1153.6	1164.2	1173.2	1156.6	1164.9
10°	1159.6	1186.1	1220.1	1239.0	1255.7	1261.7	1267.8	1274.6	1285.2	1295.0	1287.5
12.5°	1242.8	1281.4	1313.9	1348.0	1368.4	1366.1	1383.5	1388.1	1396.4	1398.6	1401.7
15°	1310.9	1365.4	1385.8	1436.5	1441.0	1456.1	1475.8	1493.2	1495.5	1490.9	1490.9
17.5°	1376.0	1422.9	1459.2	1500.0	1508.3	1521.2	1546.2	1554.5	1557.5	1556.7	1556.7
20°	1428.9	1459.9	1521.2	1555.2	1568.8	1585.5	1602.9	1613.5	1615.7	1618.8	1614.2
22.5°	1463.7	1510.6	1560.5	1588.5	1599.9	1605.9	1617.3	1620.3	1616.5	1617.3	1618.0
25°	1490.9	1537.1	1567.3	1574.9	1574.1	1566.6	1558.3	1543.9	1542.4	1536.3	1524.2
27.5°	1498.5	1515.9	1512.1	1481.1	1450.1	1447.1	1397.1	1369.9	1338.9	1343.4	1326.0
30°	1457.6	1435.0	1381.2	1302.6	1270.1	1217.1	1161.1	1102.9	1080.2	1055.2	1101.4
32.5°	1357.8	1276.9	1181.5	1079.4	1025.0	978.1	918.3	876.0	851.7	831.3	870.7
35°	1207.3	1080.9	954.6	857.8	813.2	770.8	714.8	693.6	663.4	666.4	670.2
37.5°	1013.6	874.4	779.1	683.8	654.3	636.9	596.1	563.5	553.0	549.9	549.9
40°	832.1	717.9	633.1	558.2	535.6	521.2	488.7	473.5	462.2	459.2	462.9
42.5°	688.4	590.8	525.0	475.0	459.2	441.0	427.4	408.5	406.2	400.9	407.7
45°	577.9	493.2	444.0	407.7	394.1	387.3	372.2	360.8	356.3	355.5	360.8
47.5°	490.2	424.4	381.2	358.5	348.0	341.2	328.3	323.8	319.2	320.7	318.5
50°	411.5	362.3	334.3	313.9	307.1	300.3	292.0	287.4	285.2	285.2	284.4
52.5°	353.3	312.4	294.3	275.3	272.3	268.5	259.5	256.4	252.6	251.9	254.9
55°	302.6	274.6	256.4	245.1	242.1	234.5	230.7	226.9	224.7	223.1	223.9
57.5°	258.7	237.5	225.4	215.6	210.3	207.3	200.5	199.7	198.2	198.2	197.4
60°	222.4	207.3	192.9	186.8	183.1	179.3	178.5	174.0	171.7	173.2	172.5
62.5°	188.4	176.2	167.9	161.1	158.9	155.8	153.6	152.0	149.8	150.5	150.5
65°	157.3	147.5	141.5	135.4	134.6	131.6	130.9	129.4	129.4	128.6	130.1
67.5°	129.4	122.5	117.2	113.5	111.2	112.0	108.9	106.7	106.7	105.9	108.2
70°	102.9	99.1	93.8	89.3	86.2	86.2	82.5	81.7	81.7	81.7	80.9
72.5°	79.4	72.6	70.3	68.8	68.8	68.8	67.3	67.3	66.6	67.3	66.6
75°	59.0	58.2	56.7	56.0	56.0	55.2	54.5	54.5	54.5	54.5	54.5
77.5°	46.1	46.1	44.6	43.9	43.9	43.9	43.1	43.1	42.4	42.4	42.4
80°	34.0	34.0	32.5	32.5	32.5	31.8	31.8	31.8	32.5	31.8	31.8
82.5°	23.4	23.4	22.7	23.4	22.7	21.9	21.9	21.9	21.2	21.9	21.9
85°	13.6	13.6	12.9	12.1	12.9	12.9	12.1	12.9	12.1	12.9	12.1
87.5°	5.3	4.5	4.5	4.5	3.8	4.5	3.8	3.8	4.5	3.8	4.5
90°	24.4	25.2	26.1	27.0	27.4	27.6	28.1	28.5	29.0	29.4	29.0
92.5°	27.0	28.5	30.0	31.5	32.3	32.4	32.6	32.9	33.1	33.3	33.1
95°	31.9	33.4	34.9	36.4	37.2	37.2	37.2	37.2	37.2	37.2	37.2
97.5°	33.1	34.9	36.6	38.3	39.2	39.3	39.5	39.8	40.0	40.2	40.0
100°	34.1	35.8	37.6	39.3	40.2	40.3	40.5	40.8	41.0	41.2	41.0
102.5°	65.3	58.1	51.0	43.8	40.2	40.4	40.8	41.3	41.7	42.1	41.7
105°	176.1	137.5	99.0	60.5	41.2	41.4	41.8	42.3	42.7	43.1	42.7
107.5°	347.6	314.0	280.5	247.0	230.2	215.9	187.4	158.9	130.4	101.9	130.4
110°	434.7	427.5	420.3	413.1	409.5	393.9	362.8	331.7	300.5	269.4	300.5

TEST NUMBER: P1010919

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	505.6	507.5	509.5	511.4	512.4	512.2	511.8	511.3	510.9	510.5	510.9
115°	564.6	566.8	568.9	571.1	572.2	572.6	573.5	574.4	575.2	576.1	575.2
117.5°	621.9	623.7	625.4	627.1	628.0	628.1	628.3	628.6	628.8	629.0	628.8
120°	677.8	679.5	681.3	683.0	683.9	683.9	683.9	683.9	683.9	683.9	683.9
122.5°	733.0	734.1	735.2	736.3	736.8	736.9	737.1	737.4	737.6	737.8	737.6
125°	784.2	784.7	785.1	785.6	785.8	786.0	786.4	786.9	787.3	787.7	787.3
127.5°	836.4	837.0	837.7	838.4	838.7	838.5	838.0	837.6	837.1	836.7	837.1
130°	882.7	883.5	884.4	885.3	885.7	885.5	885.0	884.6	884.1	883.7	884.1
132.5°	926.8	927.6	928.5	929.4	929.8	929.5	928.8	928.2	927.5	926.9	927.5
135°	971.6	972.2	972.9	973.6	973.9	973.6	972.9	972.2	971.6	970.9	971.6
137.5°	1011.2	1012.3	1013.4	1014.5	1015.0	1014.8	1014.4	1013.9	1013.5	1013.1	1013.5
140°	1049.2	1050.1	1051.0	1051.9	1052.3	1052.1	1051.6	1051.2	1050.7	1050.3	1050.7
142.5°	1085.2	1085.9	1086.5	1087.2	1087.5	1087.2	1086.5	1085.9	1085.2	1084.6	1085.2
145°	1118.3	1118.8	1119.2	1119.7	1119.9	1119.9	1119.9	1119.9	1119.9	1119.9	1119.9
147.5°	1148.7	1149.1	1149.6	1150.0	1150.2	1149.7	1148.6	1147.5	1146.4	1145.3	1146.4
150°	1176.1	1176.6	1177.0	1177.5	1177.7	1177.4	1176.7	1176.0	1175.4	1174.7	1175.4
152.5°	1200.1	1201.0	1201.9	1202.8	1203.2	1202.7	1201.6	1200.5	1199.4	1198.3	1199.4
155°	1221.9	1223.0	1224.1	1225.2	1225.7	1225.0	1223.7	1222.4	1221.1	1219.8	1221.1
157.5°	1241.7	1243.0	1244.3	1245.6	1246.3	1245.4	1243.7	1241.9	1240.2	1238.4	1240.2
160°	1258.3	1259.6	1260.9	1262.2	1262.9	1262.1	1260.6	1259.1	1257.6	1256.1	1257.6
162.5°	1273.2	1274.8	1276.3	1277.8	1278.6	1277.9	1276.6	1275.3	1274.0	1272.7	1274.0
165°	1286.2	1288.0	1289.7	1291.4	1292.3	1291.5	1290.0	1288.5	1287.0	1285.5	1287.0
167.5°	1297.0	1298.8	1300.5	1302.2	1303.1	1302.2	1300.5	1298.8	1297.0	1295.3	1297.0
170°	1305.8	1307.6	1309.3	1311.0	1311.9	1311.0	1309.3	1307.6	1305.8	1304.1	1305.8
172.5°	1311.7	1313.4	1315.2	1316.9	1317.8	1316.8	1314.9	1312.9	1311.0	1309.0	1311.0
175°	1316.3	1317.9	1319.4	1320.9	1321.7	1320.8	1319.1	1317.4	1315.6	1313.9	1315.6
177.5°	1318.5	1320.3	1322.0	1323.7	1324.6	1323.5	1321.3	1319.2	1317.0	1314.8	1317.0
180°	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8

TEST NUMBER: P1010919

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	953.9	949.3	946.3	944.0	941.8	948.6	939.5	929.7	922.8	918.3	916.8
5°	1053.7	1043.9	1035.6	1028.7	1030.3	1030.3	1014.4	997.0	981.9	973.5	964.5
7.5°	1169.4	1158.9	1142.2	1138.4	1135.4	1116.5	1100.6	1068.8	1049.9	1031.0	1014.4
10°	1284.4	1270.8	1254.9	1249.6	1242.1	1218.6	1194.4	1153.6	1130.1	1095.3	1073.4
12.5°	1391.8	1375.2	1359.3	1355.5	1344.2	1323.8	1282.2	1239.8	1199.7	1162.6	1124.1
15°	1481.9	1477.3	1453.1	1438.0	1413.0	1385.0	1376.0	1318.5	1267.8	1229.2	1159.6
17.5°	1557.5	1536.3	1513.6	1503.8	1494.0	1461.4	1428.9	1369.9	1315.4	1258.7	1214.1
20°	1618.0	1594.6	1578.7	1564.3	1559.8	1522.7	1471.3	1419.1	1359.3	1295.8	1237.5
22.5°	1621.0	1618.0	1607.4	1599.1	1590.0	1565.8	1525.0	1459.9	1396.4	1326.8	1250.4
25°	1558.3	1553.7	1584.0	1576.4	1582.5	1573.4	1551.4	1497.0	1422.9	1341.2	1264.0
27.5°	1369.1	1415.3	1462.9	1479.6	1490.9	1523.5	1534.0	1503.8	1444.0	1357.0	1270.8
30°	1112.0	1173.2	1250.4	1292.0	1323.8	1384.3	1462.9	1472.8	1444.8	1375.2	1269.3
32.5°	872.9	928.9	990.9	1040.1	1082.5	1206.5	1312.4	1388.8	1402.4	1366.1	1273.1
35°	703.5	727.7	786.7	833.6	891.1	997.0	1121.8	1245.1	1328.3	1332.8	1261.7
37.5°	580.2	593.0	644.5	671.0	705.0	798.0	914.5	1075.6	1205.0	1266.3	1230.0
40°	480.3	509.8	539.3	554.5	578.7	643.0	754.9	881.2	1041.6	1155.1	1180.8
42.5°	416.8	429.7	448.6	469.7	484.9	540.9	615.7	731.5	876.0	1034.0	1105.1
45°	367.6	372.2	391.8	405.4	421.3	460.7	513.6	610.4	737.5	893.3	1014.4
47.5°	326.8	335.9	346.4	354.8	365.4	395.6	441.0	511.3	623.3	762.5	892.6
50°	290.5	295.8	309.4	313.2	320.7	341.9	376.7	430.4	522.7	633.9	768.5
52.5°	256.4	266.3	271.6	276.9	283.7	301.1	323.8	367.6	437.2	541.6	655.8
55°	230.0	233.0	240.5	245.1	250.4	262.5	282.1	314.7	369.1	452.3	560.5
57.5°	204.2	204.2	211.8	215.6	220.9	230.0	247.4	272.3	311.7	373.7	472.8
60°	177.0	177.8	183.8	188.4	189.9	198.9	213.3	233.0	263.2	308.6	389.6
62.5°	152.8	156.6	159.6	161.1	166.4	171.7	183.8	197.4	218.6	258.7	316.2
65°	132.4	133.1	135.4	136.9	139.2	145.2	154.3	163.4	181.5	211.0	257.9
67.5°	108.9	112.0	115.0	115.0	117.2	120.3	129.4	136.9	150.5	167.9	199.7
70°	81.7	83.2	87.7	90.0	93.0	98.3	102.9	107.4	118.0	130.9	155.1
72.5°	68.1	68.1	69.6	70.3	70.3	74.1	80.9	85.5	90.8	99.8	116.5
75°	54.5	54.5	56.7	56.0	57.5	59.0	59.8	62.8	65.8	72.6	82.5
77.5°	43.1	43.9	43.9	44.6	44.6	45.4	46.1	47.7	49.2	53.0	57.5
80°	31.8	32.5	32.5	33.3	33.3	34.0	34.8	35.6	37.1	38.6	40.8
82.5°	21.9	22.7	22.7	23.4	22.7	23.4	24.2	24.2	25.0	26.5	27.2
85°	12.9	12.9	13.6	12.9	12.9	12.9	13.6	13.6	14.4	16.6	16.6
87.5°	3.8	4.5	3.8	4.5	4.5	4.5	4.5	5.3	5.3	6.1	6.8
90°	28.5	28.1	27.6	27.4	27.0	26.1	25.2	24.4	23.5	20.7	17.9
92.5°	32.9	32.6	32.4	32.3	31.5	30.0	28.5	27.0	25.5	23.5	21.6
95°	37.2	37.2	37.2	37.2	36.4	34.9	33.4	31.9	30.4	28.0	25.6
97.5°	39.8	39.5	39.3	39.2	38.3	36.6	34.9	33.1	31.4	42.5	53.6
100°	40.8	40.5	40.3	40.2	39.3	37.6	35.8	34.1	32.3	66.3	100.3
102.5°	41.3	40.8	40.4	40.2	43.8	51.0	58.1	65.3	72.5	110.4	148.3
105°	42.3	41.8	41.4	41.2	60.5	99.0	137.5	176.1	214.6	234.2	253.8
107.5°	158.9	187.4	215.9	230.2	247.0	280.5	314.0	347.6	381.1	377.8	374.6
110°	331.7	362.8	393.9	409.5	413.1	420.3	427.5	434.7	441.9	439.5	437.1

TEST NUMBER: P1010919

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	511.3	511.8	512.2	512.4	511.4	509.5	507.5	505.6	503.6	501.2	498.8
115°	574.4	573.5	572.6	572.2	571.1	568.9	566.8	564.6	562.4	560.4	558.5
117.5°	628.6	628.3	628.1	628.0	627.1	625.4	623.7	621.9	620.2	619.1	618.0
120°	683.9	683.9	683.9	683.9	683.0	681.3	679.5	677.8	676.0	675.4	674.7
122.5°	737.4	737.1	736.9	736.8	736.3	735.2	734.1	733.0	731.9	731.0	730.2
125°	786.9	786.4	786.0	785.8	785.6	785.1	784.7	784.2	783.8	782.9	782.1
127.5°	837.6	838.0	838.5	838.7	838.4	837.7	837.0	836.4	835.7	834.6	833.5
130°	884.6	885.0	885.5	885.7	885.3	884.4	883.5	882.7	881.8	880.9	880.1
132.5°	928.2	928.8	929.5	929.8	929.4	928.5	927.6	926.8	925.9	925.2	924.6
135°	972.2	972.9	973.6	973.9	973.6	972.9	972.2	971.6	970.9	970.0	969.2
137.5°	1013.9	1014.4	1014.8	1015.0	1014.5	1013.4	1012.3	1011.2	1010.1	1009.7	1009.3
140°	1051.2	1051.6	1052.1	1052.3	1051.9	1051.0	1050.1	1049.2	1048.3	1047.7	1047.0
142.5°	1085.9	1086.5	1087.2	1087.5	1087.2	1086.5	1085.9	1085.2	1084.6	1084.0	1083.3
145°	1119.9	1119.9	1119.9	1119.9	1119.7	1119.2	1118.8	1118.3	1117.9	1117.5	1117.1
147.5°	1147.5	1148.6	1149.7	1150.2	1150.0	1149.6	1149.1	1148.7	1148.3	1147.9	1147.4
150°	1176.0	1176.7	1177.4	1177.7	1177.5	1177.0	1176.6	1176.1	1175.7	1175.3	1174.9
152.5°	1200.5	1201.6	1202.7	1203.2	1202.8	1201.9	1201.0	1200.1	1199.2	1199.0	1198.8
155°	1222.4	1223.7	1225.0	1225.7	1225.2	1224.1	1223.0	1221.9	1220.8	1220.6	1220.4
157.5°	1241.9	1243.7	1245.4	1246.3	1245.6	1244.3	1243.0	1241.7	1240.4	1240.6	1240.8
160°	1259.1	1260.6	1262.1	1262.9	1262.2	1260.9	1259.6	1258.3	1257.0	1257.2	1257.4
162.5°	1275.3	1276.6	1277.9	1278.6	1277.8	1276.3	1274.8	1273.2	1271.7	1271.9	1272.1
165°	1288.5	1290.0	1291.5	1292.3	1291.4	1289.7	1288.0	1286.2	1284.5	1284.7	1284.9
167.5°	1298.8	1300.5	1302.2	1303.1	1302.2	1300.5	1298.8	1297.0	1295.3	1295.3	1295.3
170°	1307.6	1309.3	1311.0	1311.9	1311.0	1309.3	1307.6	1305.8	1304.1	1304.1	1304.1
172.5°	1312.9	1314.9	1316.8	1317.8	1316.9	1315.2	1313.4	1311.7	1309.9	1309.7	1309.5
175°	1317.4	1319.1	1320.8	1321.7	1320.9	1319.4	1317.9	1316.3	1314.8	1314.6	1314.4
177.5°	1319.2	1321.3	1323.5	1324.6	1323.7	1322.0	1320.3	1318.5	1316.8	1316.6	1316.4
180°	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8

TEST NUMBER: P1010919

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	914.5	910.7	907.0	907.0	898.6	891.1	887.3	888.8	884.3	878.2	872.2
5°	954.6	939.5	936.5	928.1	916.8	900.9	892.6	885.0	876.0	863.8	852.5
7.5°	991.7	972.0	961.4	953.1	931.2	909.2	891.1	879.0	863.1	844.9	831.3
10°	1040.1	1003.8	992.4	973.5	942.5	911.5	890.3	870.7	848.7	827.5	809.4
12.5°	1078.7	1037.1	1015.9	997.0	956.9	917.6	882.0	857.8	831.3	807.9	784.4
15°	1122.5	1075.6	1038.6	1015.9	965.2	917.6	877.5	843.4	813.9	785.2	764.8
17.5°	1143.7	1084.7	1068.1	1035.6	962.2	914.5	865.4	829.1	793.5	760.2	736.0
20°	1177.0	1108.2	1066.6	1044.6	979.6	909.2	851.7	810.1	773.1	737.5	711.8
22.5°	1179.3	1104.4	1077.2	1035.6	955.4	893.3	839.6	789.0	745.8	712.6	686.1
25°	1174.0	1097.6	1059.8	1026.5	959.9	884.3	815.4	765.5	723.2	684.6	653.6
27.5°	1171.7	1077.9	1042.4	1009.1	934.2	857.8	801.1	744.3	695.9	661.9	630.1
30°	1168.7	1056.7	1013.6	975.0	906.2	837.4	769.3	720.1	674.0	630.9	599.1
32.5°	1149.0	1028.0	984.1	943.3	869.1	800.3	746.6	694.4	644.5	604.4	575.6
35°	1143.0	1001.5	944.0	900.2	827.5	766.3	709.5	666.4	619.5	579.4	545.4
37.5°	1125.6	974.3	912.3	856.3	780.6	722.4	680.8	637.7	592.3	549.2	521.9
40°	1095.3	942.5	872.2	814.7	736.8	677.8	639.2	607.4	562.8	524.2	490.9
42.5°	1050.7	910.0	834.3	773.8	687.6	632.4	600.6	570.4	532.5	492.4	465.2
45°	999.2	866.9	796.5	729.2	641.5	587.7	554.5	536.3	501.5	467.5	435.7
47.5°	928.9	822.2	752.7	683.1	593.8	541.6	515.1	497.0	472.8	435.7	410.0
50°	840.4	764.8	698.9	636.9	546.9	497.0	470.5	456.9	436.5	410.0	385.0
52.5°	742.1	698.2	643.7	586.2	499.2	452.3	428.1	417.6	402.4	377.5	356.3
55°	643.0	624.1	587.0	530.3	449.3	410.7	389.6	375.9	364.6	346.4	328.3
57.5°	554.5	545.4	519.7	475.8	407.7	367.6	349.5	340.4	331.3	317.7	299.5
60°	462.9	472.8	446.3	424.4	362.3	327.5	311.7	301.8	297.3	285.2	273.8
62.5°	383.5	392.6	377.5	360.8	316.9	285.9	276.1	267.0	264.0	253.4	242.1
65°	311.7	323.0	311.7	302.6	276.1	250.4	238.3	233.7	230.7	223.9	214.8
67.5°	248.1	259.5	254.2	242.8	234.5	213.3	206.5	202.0	200.5	195.2	187.6
70°	186.8	202.7	204.2	197.4	189.9	180.0	175.5	174.0	170.2	165.7	161.1
72.5°	134.6	152.8	153.6	153.6	149.0	149.0	144.5	142.2	142.2	137.7	132.4
75°	99.1	111.2	112.7	114.2	116.5	118.8	115.7	115.7	115.0	110.4	108.2
77.5°	65.8	76.4	80.2	85.5	88.5	88.5	90.0	91.5	90.0	87.7	86.2
80°	42.4	49.9	54.5	57.5	62.0	64.3	66.6	67.3	65.8	65.1	62.8
82.5°	28.0	30.3	32.5	36.3	41.6	45.4	45.4	44.6	46.1	45.4	44.6
85°	15.9	17.4	18.2	18.9	21.9	25.7	26.5	27.2	28.7	27.2	25.7
87.5°	6.1	6.8	6.8	6.8	8.3	9.1	11.3	14.4	13.6	12.1	12.1
90°	15.0	12.2	10.8	9.7	7.5	5.4	3.2	1.0	3.2	5.4	7.5
92.5°	19.6	17.7	16.7	17.3	18.6	19.9	21.2	22.5	21.2	19.9	18.6
95°	23.2	20.8	19.6	24.1	33.0	41.9	50.9	59.8	50.9	41.9	33.0
97.5°	64.7	75.8	81.3	84.4	90.5	96.6	102.7	108.8	102.7	96.6	90.5
100°	134.2	168.2	185.2	183.0	178.7	174.3	170.0	165.6	170.0	174.3	178.7
102.5°	186.2	224.1	243.0	241.6	238.7	235.9	233.0	230.2	233.0	235.9	238.7
105°	273.3	292.9	302.7	301.5	299.1	296.8	294.4	292.0	294.4	296.8	299.1
107.5°	371.3	368.0	366.4	365.4	363.5	361.5	359.6	357.6	359.6	361.5	363.5
110°	434.7	432.3	431.1	430.2	428.5	426.8	425.0	423.3	425.0	426.8	428.5

TEST NUMBER: P1010919

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	496.4	494.0	492.8	492.0	490.5	489.0	487.5	486.0	487.5	489.0	490.5
115°	556.5	554.6	553.6	552.9	551.6	550.3	549.0	547.7	549.0	550.3	551.6
117.5°	616.9	615.8	615.3	614.5	613.0	611.5	609.9	608.4	609.9	611.5	613.0
120°	674.1	673.4	673.1	672.1	670.2	668.2	666.3	664.3	666.3	668.2	670.2
122.5°	729.3	728.4	728.0	727.2	725.7	724.2	722.6	721.1	722.6	724.2	725.7
125°	781.2	780.3	779.9	779.0	777.3	775.6	773.8	772.1	773.8	775.6	777.3
127.5°	832.4	831.3	830.8	829.9	828.2	826.5	824.7	823.0	824.7	826.5	828.2
130°	879.2	878.3	877.9	877.0	875.3	873.5	871.8	870.0	871.8	873.5	875.3
132.5°	923.9	923.2	922.9	922.0	920.3	918.6	916.8	915.1	916.8	918.6	920.3
135°	968.3	967.4	967.0	966.4	965.1	963.8	962.5	961.2	962.5	963.8	965.1
137.5°	1008.8	1008.4	1008.2	1007.3	1005.6	1003.8	1002.1	1000.3	1002.1	1003.8	1005.6
140°	1046.4	1045.7	1045.4	1044.7	1043.4	1042.1	1040.8	1039.5	1040.8	1042.1	1043.4
142.5°	1082.7	1082.0	1081.7	1081.0	1079.7	1078.4	1077.1	1075.8	1077.1	1078.4	1079.7
145°	1116.6	1116.2	1116.0	1115.2	1113.7	1112.2	1110.6	1109.1	1110.6	1112.2	1113.7
147.5°	1147.0	1146.5	1146.3	1145.8	1144.7	1143.6	1142.5	1141.4	1142.5	1143.6	1144.7
150°	1174.4	1174.0	1173.8	1173.5	1172.8	1172.1	1171.5	1170.8	1171.5	1172.1	1172.8
152.5°	1198.6	1198.4	1198.3	1198.2	1198.0	1197.7	1197.5	1197.3	1197.5	1197.7	1198.0
155°	1220.1	1219.9	1219.8	1220.0	1220.5	1220.9	1221.4	1221.8	1221.4	1220.9	1220.5
157.5°	1241.1	1241.3	1241.4	1241.4	1241.4	1241.4	1241.4	1241.4	1241.4	1241.4	1241.4
160°	1257.7	1257.9	1258.0	1258.1	1258.3	1258.6	1258.8	1259.0	1258.8	1258.6	1258.3
162.5°	1272.4	1272.6	1272.7	1273.0	1273.7	1274.4	1275.0	1275.7	1275.0	1274.4	1273.7
165°	1285.2	1285.4	1285.5	1285.8	1286.5	1287.1	1287.8	1288.4	1287.8	1287.1	1286.5
167.5°	1295.3	1295.3	1295.3	1295.7	1296.6	1297.5	1298.3	1299.2	1298.3	1297.5	1296.6
170°	1304.1	1304.1	1304.1	1304.5	1305.4	1306.3	1307.1	1308.0	1307.1	1306.3	1305.4
172.5°	1309.3	1309.1	1309.0	1309.5	1310.6	1311.7	1312.8	1313.9	1312.8	1311.7	1310.6
175°	1314.2	1314.0	1313.9	1314.4	1315.5	1316.6	1317.7	1318.8	1317.7	1316.6	1315.5
177.5°	1316.1	1315.9	1315.8	1316.3	1317.4	1318.5	1319.6	1320.7	1319.6	1318.5	1317.4
180°	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8

TEST NUMBER: P1010919

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	872.2	868.4	866.9	863.1	854.0	848.0	841.2	836.6	837.4	833.6	835.9
5°	844.9	844.2	838.9	831.3	818.5	811.7	799.6	793.5	790.5	791.2	786.7
7.5°	822.2	815.4	811.7	799.6	787.4	773.1	763.2	757.9	753.4	748.9	745.8
10°	796.5	790.5	784.4	771.6	754.9	741.3	727.7	722.4	715.6	712.6	710.3
12.5°	769.3	765.5	757.9	742.8	723.9	711.0	695.2	692.1	683.1	677.0	675.5
15°	744.3	742.1	728.4	711.0	692.1	679.3	665.7	656.6	641.5	644.5	639.2
17.5°	717.9	708.0	699.7	676.3	667.2	647.5	631.6	627.1	616.5	609.7	602.9
20°	688.4	682.3	671.7	656.6	634.6	612.0	599.9	592.3	586.2	575.6	572.6
22.5°	660.4	652.8	643.7	624.1	605.1	586.2	569.6	562.8	555.2	547.7	543.1
25°	638.4	627.1	617.2	593.0	574.1	558.2	547.7	536.3	525.7	521.2	519.7
27.5°	604.4	597.6	587.7	565.1	547.7	530.3	520.4	512.9	501.5	496.2	491.7
30°	582.5	568.8	557.5	539.3	521.9	503.0	494.0	484.9	478.1	471.3	466.0
32.5°	553.0	542.4	533.3	515.1	497.7	480.3	470.5	456.9	453.1	447.8	441.8
35°	524.2	517.4	507.6	487.9	469.0	456.9	446.3	433.4	428.9	425.1	419.8
37.5°	497.0	487.1	480.3	461.4	444.8	430.4	422.1	411.5	408.5	403.9	400.2
40°	473.5	463.7	456.9	438.0	420.6	405.4	400.2	389.6	385.0	379.7	377.5
42.5°	447.1	438.7	429.7	416.0	397.9	382.8	372.2	366.1	360.1	357.8	353.3
45°	419.1	411.5	404.7	389.6	370.7	360.1	351.0	342.7	338.1	334.3	331.3
47.5°	394.9	388.1	379.0	362.3	347.2	337.4	328.3	320.0	315.4	310.9	307.1
50°	366.9	363.1	353.3	337.4	323.0	311.7	303.3	295.8	292.7	287.4	281.4
52.5°	341.9	335.1	326.8	313.9	301.1	287.4	276.1	271.6	266.3	263.2	257.9
55°	312.4	307.9	298.8	287.4	273.8	262.5	254.2	248.1	241.3	238.3	231.5
57.5°	287.4	279.1	274.6	260.2	247.4	236.0	230.0	223.9	216.3	211.8	208.8
60°	260.2	252.6	245.8	233.7	224.7	212.6	203.5	198.2	192.9	186.8	183.8
62.5°	233.7	227.7	219.4	209.5	198.2	188.4	181.5	174.0	171.0	164.9	162.6
65°	205.0	200.5	193.6	182.3	173.2	164.9	158.1	152.0	149.0	146.7	145.2
67.5°	179.3	173.2	168.7	158.9	149.0	142.2	138.4	134.6	130.9	128.6	126.3
70°	152.8	148.3	143.7	134.6	127.8	121.8	118.8	115.7	113.5	111.2	108.9
72.5°	125.6	123.3	118.8	112.7	107.4	102.9	100.6	96.8	94.6	90.8	89.3
75°	103.6	99.8	97.6	92.3	87.7	84.0	80.9	76.4	73.4	71.9	71.1
77.5°	81.7	80.2	77.2	72.6	70.3	66.6	62.0	60.5	59.0	59.0	58.2
80°	61.3	59.0	56.7	53.0	50.7	47.7	47.7	47.7	46.9	47.7	46.9
82.5°	41.6	40.1	38.6	36.3	35.6	35.6	36.3	36.3	36.3	36.3	36.3
85°	24.2	24.2	24.2	25.0	24.2	24.2	25.0	25.7	25.0	25.0	24.2
87.5°	11.3	11.3	12.1	12.1	12.9	12.9	12.9	12.9	12.9	12.9	13.6
90°	9.7	10.8	12.2	15.0	17.9	20.7	23.5	24.4	25.2	26.1	27.0
92.5°	17.3	16.7	17.7	19.6	21.6	23.5	25.5	27.0	28.5	30.0	31.5
95°	24.1	19.6	20.8	23.2	25.6	28.0	30.4	31.9	33.4	34.9	36.4
97.5°	84.4	81.3	75.8	64.7	53.6	42.5	31.4	33.1	34.9	36.6	38.3
100°	183.0	185.2	168.2	134.2	100.3	66.3	32.3	34.1	35.8	37.6	39.3
102.5°	241.6	243.0	224.1	186.2	148.3	110.4	72.5	65.3	58.1	51.0	43.8
105°	301.5	302.7	292.9	273.3	253.8	234.2	214.6	176.1	137.5	99.0	60.5
107.5°	365.4	366.4	368.0	371.3	374.6	377.8	381.1	347.6	314.0	280.5	247.0
110°	430.2	431.1	432.3	434.7	437.1	439.5	441.9	434.7	427.5	420.3	413.1

TEST NUMBER: P1010919

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	492.0	492.8	494.0	496.4	498.8	501.2	503.6	505.6	507.5	509.5	511.4
115°	552.9	553.6	554.6	556.5	558.5	560.4	562.4	564.6	566.8	568.9	571.1
117.5°	614.5	615.3	615.8	616.9	618.0	619.1	620.2	621.9	623.7	625.4	627.1
120°	672.1	673.1	673.4	674.1	674.7	675.4	676.0	677.8	679.5	681.3	683.0
122.5°	727.2	728.0	728.4	729.3	730.2	731.0	731.9	733.0	734.1	735.2	736.3
125°	779.0	779.9	780.3	781.2	782.1	782.9	783.8	784.2	784.7	785.1	785.6
127.5°	829.9	830.8	831.3	832.4	833.5	834.6	835.7	836.4	837.0	837.7	838.4
130°	877.0	877.9	878.3	879.2	880.1	880.9	881.8	882.7	883.5	884.4	885.3
132.5°	922.0	922.9	923.2	923.9	924.6	925.2	925.9	926.8	927.6	928.5	929.4
135°	966.4	967.0	967.4	968.3	969.2	970.0	970.9	971.6	972.2	972.9	973.6
137.5°	1007.3	1008.2	1008.4	1008.8	1009.3	1009.7	1010.1	1011.2	1012.3	1013.4	1014.5
140°	1044.7	1045.4	1045.7	1046.4	1047.0	1047.7	1048.3	1049.2	1050.1	1051.0	1051.9
142.5°	1081.0	1081.7	1082.0	1082.7	1083.3	1084.0	1084.6	1085.2	1085.9	1086.5	1087.2
145°	1115.2	1116.0	1116.2	1116.6	1117.1	1117.5	1117.9	1118.3	1118.8	1119.2	1119.7
147.5°	1145.8	1146.3	1146.5	1147.0	1147.4	1147.9	1148.3	1148.7	1149.1	1149.6	1150.0
150°	1173.5	1173.8	1174.0	1174.4	1174.9	1175.3	1175.7	1176.1	1176.6	1177.0	1177.5
152.5°	1198.2	1198.3	1198.4	1198.6	1198.8	1199.0	1199.2	1200.1	1201.0	1201.9	1202.8
155°	1220.0	1219.8	1219.9	1220.1	1220.4	1220.6	1220.8	1221.9	1223.0	1224.1	1225.2
157.5°	1241.4	1241.4	1241.3	1241.1	1240.8	1240.6	1240.4	1241.7	1243.0	1244.3	1245.6
160°	1258.1	1258.0	1257.9	1257.7	1257.4	1257.2	1257.0	1258.3	1259.6	1260.9	1262.2
162.5°	1273.0	1272.7	1272.6	1272.4	1272.1	1271.9	1271.7	1273.2	1274.8	1276.3	1277.8
165°	1285.8	1285.5	1285.4	1285.2	1284.9	1284.7	1284.5	1286.2	1288.0	1289.7	1291.4
167.5°	1295.7	1295.3	1295.3	1295.3	1295.3	1295.3	1295.3	1297.0	1298.8	1300.5	1302.2
170°	1304.5	1304.1	1304.1	1304.1	1304.1	1304.1	1304.1	1305.8	1307.6	1309.3	1311.0
172.5°	1309.5	1309.0	1309.1	1309.3	1309.5	1309.7	1309.9	1311.7	1313.4	1315.2	1316.9
175°	1314.4	1313.9	1314.0	1314.2	1314.4	1314.6	1314.8	1316.3	1317.9	1319.4	1320.9
177.5°	1316.3	1315.8	1315.9	1316.1	1316.4	1316.6	1316.8	1318.5	1320.3	1322.0	1323.7
180°	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8

TEST NUMBER: P1010919

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	835.1	835.9	833.6	829.1	828.3	829.8	834.3	832.8	829.1	835.9	829.8
5°	789.0	785.2	783.7	785.2	780.6	778.4	782.9	780.6	782.9	783.7	785.9
7.5°	744.3	745.1	740.5	741.3	735.3	736.8	736.8	736.8	739.0	740.5	743.6
10°	705.8	707.3	702.0	702.7	698.2	695.2	697.4	702.0	702.0	702.0	703.5
12.5°	674.7	667.9	664.1	663.4	658.1	656.6	661.1	662.6	666.4	666.4	668.7
15°	636.2	634.6	631.6	631.6	618.8	621.8	623.3	628.6	636.2	630.1	631.6
17.5°	601.4	597.6	593.8	592.3	590.8	586.2	592.3	591.5	596.1	596.8	599.1
20°	570.4	567.3	559.8	560.5	562.0	555.2	559.0	559.0	563.5	568.1	573.4
22.5°	540.1	537.1	533.3	534.8	530.3	528.7	528.7	532.5	537.8	541.6	540.9
25°	516.6	511.3	509.1	506.8	504.5	506.1	503.8	507.6	511.3	513.6	511.3
27.5°	490.2	487.9	483.4	481.1	477.3	478.8	480.3	483.4	485.6	485.6	487.9
30°	464.5	461.4	459.9	457.6	457.6	454.6	455.4	458.4	460.7	462.9	466.0
32.5°	439.5	437.2	434.9	434.9	433.4	432.7	431.9	436.5	436.5	441.0	441.0
35°	419.1	415.3	415.3	411.5	413.0	412.3	410.7	413.8	414.5	417.6	416.8
37.5°	396.4	396.4	394.9	391.1	388.1	388.8	392.6	392.6	394.9	394.1	396.4
40°	373.7	372.2	372.2	369.9	369.1	368.4	369.1	369.9	373.7	372.9	373.7
42.5°	351.0	351.7	348.0	348.0	348.0	345.7	346.4	347.2	348.7	350.2	352.5
45°	329.0	327.5	326.8	325.3	323.8	324.5	323.8	326.8	326.0	327.5	329.8
47.5°	305.6	303.3	302.6	299.5	299.5	301.1	300.3	302.6	303.3	305.6	304.1
50°	282.9	279.9	277.6	278.4	273.8	275.3	275.3	277.6	279.9	280.6	282.1
52.5°	256.4	255.7	254.9	251.1	250.4	249.6	250.4	251.1	254.2	256.4	257.2
55°	230.7	230.0	225.4	223.9	221.6	221.6	223.1	223.9	229.2	230.0	233.0
57.5°	207.3	205.0	199.7	198.9	198.9	198.9	196.7	199.7	201.2	205.0	205.0
60°	181.5	181.5	177.0	177.0	177.8	177.0	177.0	177.8	177.8	180.8	182.3
62.5°	161.1	160.4	160.4	158.9	158.1	158.9	158.1	158.1	158.9	161.1	163.4
65°	143.0	142.2	141.5	140.7	139.2	139.2	139.9	141.5	141.5	143.0	143.7
67.5°	125.6	125.6	124.1	124.1	123.3	122.5	123.3	122.5	125.6	125.6	126.3
70°	108.2	107.4	105.1	104.4	102.1	102.9	102.9	105.1	105.9	107.4	108.9
72.5°	87.0	87.0	85.5	84.0	84.7	83.2	83.2	84.0	84.0	86.2	87.0
75°	71.9	70.3	69.6	70.3	69.6	71.1	69.6	69.6	71.1	71.1	71.1
77.5°	59.0	59.0	58.2	58.2	59.0	58.2	59.0	59.0	59.0	58.2	59.0
80°	48.4	47.7	47.7	47.7	46.9	46.9	46.9	46.9	46.9	46.9	46.9
82.5°	36.3	36.3	35.6	36.3	36.3	35.6	36.3	35.6	35.6	36.3	36.3
85°	24.2	25.7	24.2	24.2	25.0	25.0	25.7	25.0	25.7	24.2	25.0
87.5°	12.9	13.6	13.6	12.9	12.9	13.6	13.6	13.6	14.4	12.9	13.6
90°	27.4	27.6	28.1	28.5	29.0	29.4	29.0	28.5	28.1	27.6	27.4
92.5°	32.3	32.4	32.6	32.9	33.1	33.3	33.1	32.9	32.6	32.4	32.3
95°	37.2	37.2	37.2	37.2	37.2	37.2	37.2	37.2	37.2	37.2	37.2
97.5°	39.2	39.3	39.5	39.8	40.0	40.2	40.0	39.8	39.5	39.3	39.2
100°	40.2	40.3	40.5	40.8	41.0	41.2	41.0	40.8	40.5	40.3	40.2
102.5°	40.2	40.4	40.8	41.3	41.7	42.1	41.7	41.3	40.8	40.4	40.2
105°	41.2	41.4	41.8	42.3	42.7	43.1	42.7	42.3	41.8	41.4	41.2
107.5°	230.2	215.9	187.4	158.9	130.4	101.9	130.4	158.9	187.4	215.9	230.2
110°	409.5	393.9	362.8	331.7	300.5	269.4	300.5	331.7	362.8	393.9	409.5

TEST NUMBER: P1010919

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	512.4	512.2	511.8	511.3	510.9	510.5	510.9	511.3	511.8	512.2	512.4
115°	572.2	572.6	573.5	574.4	575.2	576.1	575.2	574.4	573.5	572.6	572.2
117.5°	628.0	628.1	628.3	628.6	628.8	629.0	628.8	628.6	628.3	628.1	628.0
120°	683.9	683.9	683.9	683.9	683.9	683.9	683.9	683.9	683.9	683.9	683.9
122.5°	736.8	736.9	737.1	737.4	737.6	737.8	737.6	737.4	737.1	736.9	736.8
125°	785.8	786.0	786.4	786.9	787.3	787.7	787.3	786.9	786.4	786.0	785.8
127.5°	838.7	838.5	838.0	837.6	837.1	836.7	837.1	837.6	838.0	838.5	838.7
130°	885.7	885.5	885.0	884.6	884.1	883.7	884.1	884.6	885.0	885.5	885.7
132.5°	929.8	929.5	928.8	928.2	927.5	926.9	927.5	928.2	928.8	929.5	929.8
135°	973.9	973.6	972.9	972.2	971.6	970.9	971.6	972.2	972.9	973.6	973.9
137.5°	1015.0	1014.8	1014.4	1013.9	1013.5	1013.1	1013.5	1013.9	1014.4	1014.8	1015.0
140°	1052.3	1052.1	1051.6	1051.2	1050.7	1050.3	1050.7	1051.2	1051.6	1052.1	1052.3
142.5°	1087.5	1087.2	1086.5	1085.9	1085.2	1084.6	1085.2	1085.9	1086.5	1087.2	1087.5
145°	1119.9	1119.9	1119.9	1119.9	1119.9	1119.9	1119.9	1119.9	1119.9	1119.9	1119.9
147.5°	1150.2	1149.7	1148.6	1147.5	1146.4	1145.3	1146.4	1147.5	1148.6	1149.7	1150.2
150°	1177.7	1177.4	1176.7	1176.0	1175.4	1174.7	1175.4	1176.0	1176.7	1177.4	1177.7
152.5°	1203.2	1202.7	1201.6	1200.5	1199.4	1198.3	1199.4	1200.5	1201.6	1202.7	1203.2
155°	1225.7	1225.0	1223.7	1222.4	1221.1	1219.8	1221.1	1222.4	1223.7	1225.0	1225.7
157.5°	1246.3	1245.4	1243.7	1241.9	1240.2	1238.4	1240.2	1241.9	1243.7	1245.4	1246.3
160°	1262.9	1262.1	1260.6	1259.1	1257.6	1256.1	1257.6	1259.1	1260.6	1262.1	1262.9
162.5°	1278.6	1277.9	1276.6	1275.3	1274.0	1272.7	1274.0	1275.3	1276.6	1277.9	1278.6
165°	1292.3	1291.5	1290.0	1288.5	1287.0	1285.5	1287.0	1288.5	1290.0	1291.5	1292.3
167.5°	1303.1	1302.2	1300.5	1298.8	1297.0	1295.3	1297.0	1298.8	1300.5	1302.2	1303.1
170°	1311.9	1311.0	1309.3	1307.6	1305.8	1304.1	1305.8	1307.6	1309.3	1311.0	1311.9
172.5°	1317.8	1316.8	1314.9	1312.9	1311.0	1309.0	1311.0	1312.9	1314.9	1316.8	1317.8
175°	1321.7	1320.8	1319.1	1317.4	1315.6	1313.9	1315.6	1317.4	1319.1	1320.8	1321.7
177.5°	1324.6	1323.5	1321.3	1319.2	1317.0	1314.8	1317.0	1319.2	1321.3	1323.5	1324.6
180°	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8

TEST NUMBER: P1010919

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	835.9	838.9	835.9	829.8	835.9	839.6	843.4	849.5	852.5	852.5	857.0
5°	788.2	794.3	792.0	790.5	796.5	800.3	806.4	813.9	822.2	827.5	833.6
7.5°	745.8	749.6	753.4	753.4	759.5	767.8	776.9	785.9	796.5	804.1	808.6
10°	708.8	711.8	714.1	717.1	726.2	735.3	747.4	758.7	767.8	776.1	783.7
12.5°	673.2	677.8	683.1	685.3	692.1	703.5	714.8	728.4	742.8	751.1	758.7
15°	639.2	641.5	647.5	654.3	660.4	672.5	686.8	701.2	713.3	726.2	733.0
17.5°	604.4	605.1	621.0	617.2	636.9	648.3	655.8	669.4	689.1	699.7	710.3
20°	570.4	577.9	584.7	588.5	599.1	612.0	633.9	644.5	660.4	670.2	679.3
22.5°	543.9	555.2	555.2	564.3	569.6	581.7	597.6	618.0	635.4	642.2	655.1
25°	520.4	525.7	534.8	537.8	547.7	558.2	568.8	590.8	609.7	618.8	627.8
27.5°	490.2	497.0	509.1	509.1	521.9	533.3	546.1	560.5	579.4	592.3	602.1
30°	466.7	473.5	478.8	487.1	492.4	503.0	525.7	536.3	553.0	564.3	576.4
32.5°	444.8	450.1	454.6	463.7	469.7	481.8	494.0	512.9	527.2	537.8	550.7
35°	420.6	425.9	431.9	438.7	447.8	459.2	470.5	486.4	500.8	510.6	521.2
37.5°	397.9	401.7	410.7	415.3	422.8	433.4	447.8	464.5	477.3	484.9	495.5
40°	375.9	379.0	385.8	394.1	399.4	407.7	422.8	437.2	453.1	462.2	470.5
42.5°	352.5	356.3	362.3	370.7	379.0	388.1	396.4	413.0	427.4	434.9	444.0
45°	332.1	334.3	338.9	347.2	355.5	362.3	375.2	390.3	403.9	410.0	419.8
47.5°	307.9	310.1	316.9	320.7	329.8	338.9	351.7	366.9	379.0	385.0	394.1
50°	282.9	285.2	289.7	298.0	304.1	313.9	325.3	338.1	353.3	361.6	366.9
52.5°	258.7	263.2	267.0	273.8	281.4	291.2	301.8	313.9	326.8	335.1	341.2
55°	234.5	238.3	242.8	246.6	255.7	264.8	276.9	288.2	299.5	307.1	313.9
57.5°	207.3	212.6	217.1	224.7	231.5	239.0	252.6	261.7	275.3	280.6	286.7
60°	183.8	189.1	192.9	198.9	205.0	214.8	223.9	235.3	246.6	253.4	261.0
62.5°	164.1	166.4	168.7	174.7	180.8	189.9	198.9	210.3	222.4	226.2	232.2
65°	144.5	146.7	150.5	155.8	160.4	165.7	175.5	184.6	195.9	202.0	204.2
67.5°	127.8	130.1	130.9	134.6	138.4	144.5	149.8	158.9	169.4	173.2	177.8
70°	108.9	112.7	113.5	116.5	118.0	121.8	127.8	134.6	143.0	149.8	153.6
72.5°	87.0	92.3	93.8	98.3	100.6	104.4	108.9	114.2	119.5	122.5	125.6
75°	71.1	72.6	73.4	77.2	80.9	86.2	88.5	91.5	96.1	99.8	102.9
77.5°	59.0	59.8	60.5	60.5	61.3	64.3	68.8	72.6	75.6	77.2	79.4
80°	47.7	46.9	46.9	47.7	47.7	47.7	49.2	54.5	56.0	59.8	59.0
82.5°	37.1	35.6	36.3	35.6	35.6	35.6	35.6	36.3	36.3	38.6	40.1
85°	24.2	25.0	24.2	24.2	23.4	24.2	23.4	23.4	22.7	22.7	21.9
87.5°	12.9	13.6	12.9	12.9	12.1	12.9	12.1	12.1	11.3	11.3	9.8
90°	27.0	26.1	25.2	24.4	23.5	20.7	17.9	15.0	12.2	10.8	9.7
92.5°	31.5	30.0	28.5	27.0	25.5	23.5	21.6	19.6	17.7	16.7	17.3
95°	36.4	34.9	33.4	31.9	30.4	28.0	25.6	23.2	20.8	19.6	24.1
97.5°	38.3	36.6	34.9	33.1	31.4	42.5	53.6	64.7	75.8	81.3	84.4
100°	39.3	37.6	35.8	34.1	32.3	66.3	100.3	134.2	168.2	185.2	183.0
102.5°	43.8	51.0	58.1	65.3	72.5	110.4	148.3	186.2	224.1	243.0	241.6
105°	60.5	99.0	137.5	176.1	214.6	234.2	253.8	273.3	292.9	302.7	301.5
107.5°	247.0	280.5	314.0	347.6	381.1	377.8	374.6	371.3	368.0	366.4	365.4
110°	413.1	420.3	427.5	434.7	441.9	439.5	437.1	434.7	432.3	431.1	430.2

TEST NUMBER: P1010919

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	511.4	509.5	507.5	505.6	503.6	501.2	498.8	496.4	494.0	492.8	492.0
115°	571.1	568.9	566.8	564.6	562.4	560.4	558.5	556.5	554.6	553.6	552.9
117.5°	627.1	625.4	623.7	621.9	620.2	619.1	618.0	616.9	615.8	615.3	614.5
120°	683.0	681.3	679.5	677.8	676.0	675.4	674.7	674.1	673.4	673.1	672.1
122.5°	736.3	735.2	734.1	733.0	731.9	731.0	730.2	729.3	728.4	728.0	727.2
125°	785.6	785.1	784.7	784.2	783.8	782.9	782.1	781.2	780.3	779.9	779.0
127.5°	838.4	837.7	837.0	836.4	835.7	834.6	833.5	832.4	831.3	830.8	829.9
130°	885.3	884.4	883.5	882.7	881.8	880.9	880.1	879.2	878.3	877.9	877.0
132.5°	929.4	928.5	927.6	926.8	925.9	925.2	924.6	923.9	923.2	922.9	922.0
135°	973.6	972.9	972.2	971.6	970.9	970.0	969.2	968.3	967.4	967.0	966.4
137.5°	1014.5	1013.4	1012.3	1011.2	1010.1	1009.7	1009.3	1008.8	1008.4	1008.2	1007.3
140°	1051.9	1051.0	1050.1	1049.2	1048.3	1047.7	1047.0	1046.4	1045.7	1045.4	1044.7
142.5°	1087.2	1086.5	1085.9	1085.2	1084.6	1084.0	1083.3	1082.7	1082.0	1081.7	1081.0
145°	1119.7	1119.2	1118.8	1118.3	1117.9	1117.5	1117.1	1116.6	1116.2	1116.0	1115.2
147.5°	1150.0	1149.6	1149.1	1148.7	1148.3	1147.9	1147.4	1147.0	1146.5	1146.3	1145.8
150°	1177.5	1177.0	1176.6	1176.1	1175.7	1175.3	1174.9	1174.4	1174.0	1173.8	1173.5
152.5°	1202.8	1201.9	1201.0	1200.1	1199.2	1199.0	1198.8	1198.6	1198.4	1198.3	1198.2
155°	1225.2	1224.1	1223.0	1221.9	1220.8	1220.6	1220.4	1220.1	1219.9	1219.8	1220.0
157.5°	1245.6	1244.3	1243.0	1241.7	1240.4	1240.6	1240.8	1241.1	1241.3	1241.4	1241.4
160°	1262.2	1260.9	1259.6	1258.3	1257.0	1257.2	1257.4	1257.7	1257.9	1258.0	1258.1
162.5°	1277.8	1276.3	1274.8	1273.2	1271.7	1271.9	1272.1	1272.4	1272.6	1272.7	1273.0
165°	1291.4	1289.7	1288.0	1286.2	1284.5	1284.7	1284.9	1285.2	1285.4	1285.5	1285.8
167.5°	1302.2	1300.5	1298.8	1297.0	1295.3	1295.3	1295.3	1295.3	1295.3	1295.3	1295.7
170°	1311.0	1309.3	1307.6	1305.8	1304.1	1304.1	1304.1	1304.1	1304.1	1304.1	1304.5
172.5°	1316.9	1315.2	1313.4	1311.7	1309.9	1309.7	1309.5	1309.3	1309.1	1309.0	1309.5
175°	1320.9	1319.4	1317.9	1316.3	1314.8	1314.6	1314.4	1314.2	1314.0	1313.9	1314.4
177.5°	1323.7	1322.0	1320.3	1318.5	1316.8	1316.6	1316.4	1316.1	1315.9	1315.8	1316.3
180°	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8	1318.8

TEST NUMBER: P1010919

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	883.5	883.5	883.5	883.5
2.5°	860.8	866.1	876.7	885.8
5°	842.7	851.0	866.9	882.8
7.5°	820.7	833.6	854.0	876.0
10°	799.6	816.2	841.2	866.9
12.5°	778.4	795.8	822.2	855.5
15°	753.4	771.6	803.3	843.4
17.5°	731.5	755.7	784.4	824.5
20°	708.0	726.2	763.2	805.6
22.5°	678.5	708.8	743.6	788.2
25°	655.1	681.5	716.3	767.0
27.5°	626.3	657.3	699.7	744.3
30°	602.9	628.6	667.9	721.6
32.5°	575.6	605.9	646.8	699.7
35°	551.4	577.2	615.7	669.4
37.5°	522.7	550.7	593.8	641.5
40°	497.7	525.0	565.8	610.4
42.5°	467.5	496.2	537.1	574.9
45°	443.3	469.7	502.3	537.1
47.5°	413.8	441.8	473.5	497.7
50°	387.3	413.0	438.0	458.4
52.5°	358.5	382.0	404.7	419.8
55°	332.1	350.2	368.4	379.0
57.5°	301.1	318.5	333.6	339.6
60°	273.8	288.2	298.0	304.8
62.5°	245.1	255.7	263.2	267.0
65°	217.1	224.7	228.4	232.2
67.5°	188.4	195.2	197.4	202.0
70°	158.1	165.7	167.2	169.4
72.5°	135.4	135.4	138.4	141.5
75°	108.2	109.7	111.2	111.2
77.5°	84.7	84.7	86.2	87.0
80°	62.0	62.8	62.8	62.0
82.5°	42.4	43.9	42.4	41.6
85°	23.4	26.5	25.0	25.0
87.5°	9.8	9.8	11.3	9.8
90°	7.5	5.4	3.2	1.0
92.5°	18.6	19.9	21.2	22.5
95°	33.0	41.9	50.9	59.8
97.5°	90.5	96.6	102.7	108.8
100°	178.7	174.3	170.0	165.6
102.5°	238.7	235.9	233.0	230.2
105°	299.1	296.8	294.4	292.0
107.5°	363.5	361.5	359.6	357.6
110°	428.5	426.8	425.0	423.3

TEST NUMBER: P1010919

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	490.5	489.0	487.5	486.0
115°	551.6	550.3	549.0	547.7
117.5°	613.0	611.5	609.9	608.4
120°	670.2	668.2	666.3	664.3
122.5°	725.7	724.2	722.6	721.1
125°	777.3	775.6	773.8	772.1
127.5°	828.2	826.5	824.7	823.0
130°	875.3	873.5	871.8	870.0
132.5°	920.3	918.6	916.8	915.1
135°	965.1	963.8	962.5	961.2
137.5°	1005.6	1003.8	1002.1	1000.3
140°	1043.4	1042.1	1040.8	1039.5
142.5°	1079.7	1078.4	1077.1	1075.8
145°	1113.7	1112.2	1110.6	1109.1
147.5°	1144.7	1143.6	1142.5	1141.4
150°	1172.8	1172.1	1171.5	1170.8
152.5°	1198.0	1197.7	1197.5	1197.3
155°	1220.5	1220.9	1221.4	1221.8
157.5°	1241.4	1241.4	1241.4	1241.4
160°	1258.3	1258.6	1258.8	1259.0
162.5°	1273.7	1274.4	1275.0	1275.7
165°	1286.5	1287.1	1287.8	1288.4
167.5°	1296.6	1297.5	1298.3	1299.2
170°	1305.4	1306.3	1307.1	1308.0
172.5°	1310.6	1311.7	1312.8	1313.9
175°	1315.5	1316.6	1317.7	1318.8
177.5°	1317.4	1318.5	1319.6	1320.7
180°	1318.8	1318.8	1318.8	1318.8

(END OF REPORT)