

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010950

Luminaire Tested: S123RDIP-B560D585UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010950
REPORT IS A COMBINATION OF REPORTS P993446 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D585UB2750-4F0-XX-W2A-A_3000K
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4566.0 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010950

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010950

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55			49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	49	48	47			42
2	90	83	77	72	82	76	71	67	65	61	58	54	52	49	44	42	41			36
3	82	73	66	61	76	68	62	57	58	53	49	48	45	42	40	37	35			31
4	75	65	58	52	69	60	54	49	52	47	43	43	40	37	36	33	31			27
5	69	58	50	45	64	54	47	42	46	41	37	39	35	32	32	30	27			24
6	64	52	45	39	59	49	42	37	42	37	33	36	32	28	30	27	24			21
7	59	47	40	34	55	44	37	33	38	33	29	33	28	25	27	24	22			19
8	55	43	36	31	51	40	34	29	35	30	26	30	26	23	25	22	20			17
9	51	40	32	27	47	37	30	26	32	27	23	28	23	20	23	20	18			16
10	48	36	29	25	44	34	28	23	30	25	21	25	21	19	22	18	16			14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9592	9592	9592	9592
5°	9600	11047	9625	8196
10°	9515	13336	9557	7159
15°	9417	15136	9417	6313
20°	9224	16325	9275	5599
25°	9082	15511	9064	5109
30°	8918	10746	8899	4630
35°	8720	6900	8681	4268
40°	8474	4872	8432	3909
45°	8045	3899	8033	3559
50°	7519	3261	7493	3149
55°	6925	2688	6871	2669
60°	6345	2222	6281	2270
65°	5661	1778	5700	1925
70°	5033	1235	5168	1556
75°	4268	916	4439	1196
80°	3399	607	3686	897
85°	2421	288	2641	559

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 12806 cd/sqm

TEST NUMBER: P1010950

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.5	1.9
10°-20°	274.0	6.0
20°-30°	431.5	9.4
30°-40°	448.7	9.8
40°-50°	383.8	8.4
50°-60°	292.6	6.4
60°-70°	187.5	4.1
70°-80°	89.8	2.0
80°-90°	25.2	0.6
90°-100°	27.1	0.6
100°-110°	131.2	2.9
110°-120°	321.4	7.0
120°-130°	408.1	8.9
130°-140°	435.9	9.5
140°-150°	407.6	8.9
150°-160°	328.8	7.2
160°-170°	212.2	4.6
170°-180°	73.1	1.6
0°-30°	792.9	17.4
0°-40°	1241.6	27.2
0°-60°	1918.1	42.0
0°-90°	2220.5	48.6
90°-120°	479.7	10.5
90°-150°	1731.4	37.9
90°-180°	2345.0	51.4
0°-180°	4566.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	891	891	891	891	891	
5°	890	1058	893	785	890	84
15°	851	1504	851	627	851	239
25°	774	1550	772	510	774	356
35°	675	672	672	416	675	423
45°	542	359	541	327	542	417
55°	382	225	379	224	382	343
65°	234	130	236	140	234	234
75°	112	55	117	72	112	121
85°	25	13	28	25	25	28
90°	1	17	1	17	1	3
95°	35	22	35	22	35	42
105°	170	25	170	25	170	181
115°	320	336	320	336	320	316
125°	450	460	450	460	450	402
135°	561	566	561	566	561	432
145°	647	653	647	653	647	405
155°	713	712	713	712	713	328
165°	752	750	752	750	752	212
175°	769	766	769	766	769	73
180°	769	769	769	769	769	

TEST NUMBER: P1010950

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1
2.5°	893.4	899.5	904.1	907.2	914.8	919.4	923.2	930.1	930.1	931.6	934.6
5°	890.4	903.4	912.5	924.7	940.7	948.4	959.0	968.2	981.2	988.0	994.9
7.5°	883.5	901.8	920.9	939.2	962.9	978.1	988.8	1012.5	1029.2	1049.8	1065.9
10°	874.4	899.5	924.0	952.2	984.2	1007.1	1023.1	1054.4	1086.5	1115.5	1139.9
12.5°	862.9	893.4	928.5	962.9	1007.9	1030.8	1056.7	1095.6	1141.4	1178.0	1210.8
15°	850.7	885.8	925.5	967.4	1023.9	1055.9	1093.3	1140.6	1191.8	1244.4	1289.4
17.5°	831.6	875.9	920.1	981.2	1047.6	1066.6	1098.7	1163.5	1226.9	1274.2	1329.1
20°	812.6	862.2	917.8	972.8	1044.5	1088.8	1118.5	1187.2	1255.1	1312.3	1364.9
22.5°	795.0	846.9	904.9	974.3	1041.4	1085.7	1123.1	1194.8	1273.4	1337.5	1402.3
25°	773.6	830.1	894.2	959.8	1041.4	1075.0	1116.2	1199.4	1282.5	1356.6	1436.7
27.5°	750.8	808.0	871.3	938.4	1013.2	1062.8	1103.2	1192.5	1294.0	1373.3	1455.7
30°	727.9	786.6	847.7	907.9	991.9	1039.2	1085.7	1184.1	1300.1	1390.9	1454.2
32.5°	705.7	755.3	815.6	874.4	957.5	1009.4	1062.0	1175.7	1302.4	1378.7	1409.2
35°	675.2	727.1	775.9	838.5	922.4	973.5	1035.3	1175.0	1292.5	1339.8	1324.5
37.5°	647.0	690.5	737.0	792.7	878.9	945.3	1009.4	1155.1	1259.7	1262.7	1176.5
40°	615.7	651.6	690.5	749.2	842.3	907.9	977.4	1124.6	1200.1	1155.1	1003.3
42.5°	579.9	611.9	642.4	699.6	801.1	874.4	949.1	1086.5	1113.9	1010.2	852.2
45°	541.7	567.6	595.9	656.2	757.6	830.1	904.9	1027.7	999.5	853.0	702.7
47.5°	502.0	524.2	551.6	606.6	711.1	785.1	856.0	943.8	872.1	714.9	589.0
50°	462.4	479.9	506.6	563.1	663.8	730.9	796.5	853.8	753.0	613.4	486.8
52.5°	423.4	437.2	464.6	512.7	610.4	674.5	721.8	743.9	641.7	506.6	422.7
55°	382.2	397.5	415.8	464.6	561.5	608.8	640.1	639.4	534.1	429.6	349.4
57.5°	342.6	356.3	372.3	421.2	499.7	531.8	558.5	545.5	445.6	351.7	299.8
60°	307.5	315.1	332.7	373.9	433.4	460.8	476.1	454.0	363.9	296.8	248.0
62.5°	269.3	277.0	291.5	330.4	367.0	381.5	394.5	366.2	300.6	241.9	212.1
65°	234.2	244.1	253.3	284.6	304.4	322.0	320.4	296.8	235.0	196.8	172.4
67.5°	203.7	207.5	215.2	234.2	243.4	256.4	257.1	230.4	189.2	160.2	145.7
70°	170.9	174.7	180.1	189.2	195.3	198.4	196.8	173.2	142.7	125.1	112.2
72.5°	142.7	141.9	145.7	145.7	151.8	151.1	146.5	128.2	108.3	93.8	86.2
75°	112.2	112.9	113.7	112.2	109.9	106.8	103.0	89.3	76.3	69.4	62.6
77.5°	87.7	86.2	87.0	81.6	78.6	75.5	70.2	63.3	52.6	51.1	48.1
80°	62.6	61.8	61.0	58.7	51.9	48.8	45.0	41.2	38.9	37.4	36.6
82.5°	42.0	42.0	40.4	35.9	32.0	29.8	29.0	27.5	25.2	25.2	24.4
85°	25.2	24.4	22.9	18.3	16.0	16.0	16.0	16.0	14.5	14.5	13.7
87.5°	9.9	9.2	6.9	6.9	6.1	6.1	6.1	5.3	5.3	4.6	4.6
90°	0.6	1.9	3.1	4.4	5.7	6.3	7.1	8.8	10.4	12.1	13.7
92.5°	13.1	12.3	11.6	10.8	10.1	9.7	10.3	11.4	12.6	13.7	14.9
95°	34.9	29.7	24.5	19.2	14.0	11.4	12.1	13.5	14.9	16.3	17.7
97.5°	63.4	59.8	56.3	52.7	49.2	47.4	44.2	37.7	31.2	24.8	18.3
100°	96.6	99.1	101.7	104.2	106.7	108.0	98.1	78.3	58.5	38.7	18.9
102.5°	134.3	136.0	137.6	139.3	141.0	141.8	130.7	108.6	86.5	64.4	42.3
105°	170.3	171.7	173.1	174.5	175.9	176.6	170.9	159.5	148.0	136.6	125.2
107.5°	208.6	209.8	210.9	212.1	213.2	213.8	214.7	216.6	218.5	220.4	222.3
110°	246.9	247.9	248.9	250.0	251.0	251.5	252.2	253.6	255.0	256.4	257.8



TEST NUMBER: P1010950

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	283.5	284.4	285.3	286.2	287.1	287.5	288.2	289.6	291.0	292.4	293.8
115°	319.5	320.3	321.0	321.8	322.5	322.9	323.5	324.6	325.8	326.9	328.1
117.5°	355.0	355.9	356.8	357.7	358.6	359.0	359.3	359.9	360.6	361.2	361.8
120°	387.5	388.7	389.8	391.0	392.1	392.7	392.9	393.3	393.6	394.0	394.4
122.5°	420.7	421.6	422.5	423.4	424.3	424.7	425.0	425.5	426.0	426.5	427.0
125°	450.4	451.4	452.4	453.5	454.5	455.0	455.3	455.8	456.3	456.8	457.3
127.5°	480.1	481.1	482.1	483.2	484.2	484.7	485.0	485.7	486.3	487.0	487.6
130°	507.6	508.6	509.6	510.6	511.6	512.1	512.4	512.9	513.4	513.9	514.4
132.5°	533.9	534.9	535.9	536.9	537.9	538.4	538.6	539.0	539.4	539.8	540.2
135°	560.7	561.5	562.3	563.0	563.8	564.2	564.4	564.9	565.4	565.9	566.4
137.5°	583.6	584.6	585.6	586.7	587.7	588.2	588.3	588.6	588.8	589.1	589.3
140°	606.5	607.3	608.0	608.8	609.5	609.9	610.1	610.5	610.8	611.2	611.6
142.5°	627.6	628.4	629.1	629.9	630.6	631.0	631.2	631.6	632.0	632.4	632.8
145°	647.0	647.9	648.8	649.7	650.6	651.0	651.1	651.4	651.7	651.9	652.2
147.5°	665.9	666.5	667.2	667.8	668.5	668.8	668.9	669.2	669.4	669.7	669.9
150°	683.1	683.5	683.9	684.2	684.6	684.8	684.9	685.2	685.4	685.7	685.9
152.5°	698.5	698.6	698.8	698.9	699.0	699.1	699.2	699.3	699.4	699.5	699.6
155°	712.8	712.5	712.3	712.0	711.7	711.6	711.7	711.8	711.9	712.1	712.2
157.5°	724.2	724.2	724.2	724.2	724.2	724.2	724.1	724.0	723.9	723.7	723.6
160°	734.5	734.4	734.2	734.1	734.0	733.9	733.8	733.7	733.6	733.5	733.4
162.5°	744.2	743.8	743.4	743.1	742.7	742.5	742.4	742.3	742.2	742.0	741.9
165°	751.6	751.2	750.8	750.5	750.1	749.9	749.8	749.7	749.6	749.5	749.4
167.5°	757.9	757.4	756.9	756.4	755.9	755.6	755.6	755.6	755.6	755.6	755.6
170°	763.1	762.6	762.1	761.6	761.1	760.8	760.8	760.8	760.8	760.8	760.8
172.5°	766.5	765.9	765.2	764.6	763.9	763.6	763.7	763.8	763.9	764.1	764.2
175°	769.4	768.8	768.1	767.5	766.8	766.5	766.6	766.7	766.8	767.0	767.1
177.5°	770.5	769.9	769.2	768.6	767.9	767.6	767.7	767.8	767.9	768.1	768.2
180°	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4

TEST NUMBER: P1010950

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1
2.5°	940.7	940.7	947.6	954.5	950.7	952.9	961.3	958.3	964.4	963.6	965.9
5°	1011.7	1020.1	1027.0	1041.4	1043.7	1041.4	1055.9	1059.8	1066.6	1058.2	1062.0
7.5°	1091.8	1109.4	1126.1	1147.5	1154.4	1155.9	1163.5	1174.2	1183.4	1166.6	1175.0
10°	1169.6	1196.3	1230.7	1249.7	1266.5	1272.6	1278.7	1285.6	1296.3	1306.2	1298.6
12.5°	1253.6	1292.5	1325.3	1359.6	1380.2	1377.9	1395.5	1400.0	1408.4	1410.7	1413.8
15°	1322.2	1377.2	1397.8	1448.9	1453.5	1468.7	1488.5	1506.1	1508.4	1503.8	1503.8
17.5°	1387.8	1435.1	1471.8	1513.0	1521.4	1534.3	1559.5	1567.9	1570.9	1570.2	1570.2
20°	1441.2	1472.5	1534.3	1568.7	1582.4	1599.2	1616.7	1627.4	1629.7	1632.7	1628.2
22.5°	1476.3	1523.6	1574.0	1602.2	1613.7	1619.8	1631.2	1634.3	1630.5	1631.2	1632.0
25°	1503.8	1550.3	1580.9	1588.5	1587.7	1580.1	1571.7	1557.2	1555.7	1549.6	1537.4
27.5°	1511.4	1529.0	1525.2	1493.9	1462.6	1459.6	1409.2	1381.7	1350.5	1355.0	1337.5
30°	1470.2	1447.3	1393.2	1313.8	1281.0	1227.6	1171.2	1112.4	1089.5	1064.3	1110.9
32.5°	1369.5	1287.9	1191.8	1088.8	1033.8	986.5	926.2	883.5	859.1	838.5	878.2
35°	1217.7	1090.3	962.9	865.2	820.2	777.5	721.0	699.6	669.1	672.2	676.0
37.5°	1022.4	882.0	785.9	689.7	660.0	642.4	601.2	568.4	557.7	554.7	554.7
40°	839.3	724.1	638.6	563.1	540.2	525.7	492.9	477.6	466.2	463.1	466.9
42.5°	694.3	595.9	529.5	479.1	463.1	444.8	431.1	412.0	409.7	404.4	411.2
45°	582.9	497.5	447.9	411.2	397.5	390.6	375.4	363.9	359.4	358.6	363.9
47.5°	494.4	428.0	384.5	361.6	351.0	344.1	331.1	326.5	322.0	323.5	321.2
50°	415.1	365.5	337.2	316.6	309.8	302.9	294.5	289.9	287.6	287.6	286.9
52.5°	356.3	315.1	296.8	277.7	274.7	270.9	261.7	258.6	254.8	254.1	257.1
55°	305.2	277.0	258.6	247.2	244.1	236.5	232.7	228.9	226.6	225.1	225.8
57.5°	260.9	239.6	227.4	217.4	212.1	209.1	202.2	201.4	199.9	199.9	199.1
60°	224.3	209.1	194.6	188.5	184.6	180.8	180.1	175.5	173.2	174.7	174.0
62.5°	190.0	177.8	169.4	162.5	160.2	157.2	154.9	153.4	151.1	151.8	151.8
65°	158.7	148.8	142.7	136.6	135.8	132.8	132.0	130.5	130.5	129.7	131.2
67.5°	130.5	123.6	118.3	114.4	112.2	112.9	109.9	107.6	107.6	106.8	109.1
70°	103.8	99.9	94.6	90.0	87.0	87.0	83.2	82.4	82.4	82.4	81.6
72.5°	80.1	73.2	71.0	69.4	69.4	69.4	67.9	67.9	67.1	67.9	67.1
75°	59.5	58.7	57.2	56.5	56.5	55.7	54.9	54.9	54.9	54.9	54.9
77.5°	46.5	46.5	45.0	44.3	44.3	44.3	43.5	43.5	42.7	42.7	42.7
80°	34.3	34.3	32.8	32.8	32.8	32.0	32.0	32.0	32.8	32.0	32.0
82.5°	23.7	23.7	22.9	23.7	22.9	22.1	22.1	22.1	21.4	22.1	22.1
85°	13.7	13.7	13.0	12.2	13.0	13.0	12.2	13.0	12.2	13.0	12.2
87.5°	5.3	4.6	4.6	4.6	3.8	4.6	3.8	3.8	4.6	3.8	4.6
90°	14.2	14.7	15.2	15.7	16.0	16.1	16.4	16.6	16.9	17.1	16.9
92.5°	15.8	16.7	17.6	18.5	18.9	19.0	19.1	19.2	19.3	19.4	19.3
95°	18.6	19.5	20.4	21.3	21.7	21.7	21.7	21.7	21.7	21.7	21.7
97.5°	19.3	20.3	21.4	22.4	22.9	23.0	23.1	23.2	23.3	23.4	23.3
100°	19.9	20.9	21.9	22.9	23.4	23.5	23.6	23.7	23.9	24.0	23.9
102.5°	38.1	33.9	29.7	25.5	23.4	23.5	23.8	24.1	24.3	24.6	24.3
105°	102.7	80.2	57.7	35.2	24.0	24.1	24.4	24.7	24.9	25.2	24.9
107.5°	202.7	183.2	163.6	144.1	134.3	126.0	109.3	92.7	76.0	59.4	76.0
110°	253.6	249.4	245.2	241.0	238.9	229.8	211.7	193.5	175.4	157.2	175.4

TEST NUMBER: P1010950

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	294.9	296.1	297.2	298.3	298.9	298.8	298.5	298.3	298.0	297.8	298.0
115°	329.4	330.6	331.9	333.2	333.8	334.1	334.6	335.1	335.6	336.1	335.6
117.5°	362.8	363.8	364.9	365.9	366.4	366.5	366.6	366.7	366.9	367.0	366.9
120°	395.4	396.4	397.5	398.5	399.0	399.0	399.0	399.0	399.0	399.0	399.0
122.5°	427.6	428.2	428.9	429.5	429.8	429.9	430.0	430.1	430.3	430.4	430.3
125°	457.5	457.8	458.0	458.3	458.4	458.5	458.8	459.1	459.3	459.6	459.3
127.5°	488.0	488.4	488.7	489.1	489.3	489.2	488.9	488.6	488.4	488.1	488.4
130°	514.9	515.4	515.9	516.4	516.7	516.6	516.3	516.1	515.8	515.6	515.8
132.5°	540.7	541.2	541.7	542.2	542.4	542.2	541.8	541.5	541.1	540.7	541.1
135°	566.8	567.2	567.6	568.0	568.2	568.0	567.6	567.2	566.8	566.4	566.8
137.5°	589.9	590.6	591.2	591.9	592.2	592.1	591.8	591.5	591.3	591.0	591.3
140°	612.1	612.6	613.1	613.6	613.9	613.8	613.5	613.2	613.0	612.7	613.0
142.5°	633.2	633.6	633.9	634.3	634.5	634.3	633.9	633.6	633.2	632.8	633.2
145°	652.4	652.7	652.9	653.2	653.3	653.3	653.3	653.3	653.3	653.3	653.3
147.5°	670.1	670.4	670.6	670.9	671.0	670.7	670.1	669.4	668.8	668.2	668.8
150°	686.2	686.4	686.7	687.0	687.1	686.9	686.5	686.1	685.7	685.3	685.7
152.5°	700.1	700.6	701.1	701.6	701.9	701.6	701.0	700.3	699.7	699.1	699.7
155°	712.8	713.5	714.1	714.8	715.1	714.7	713.9	713.2	712.4	711.6	712.4
157.5°	724.4	725.2	725.9	726.7	727.1	726.6	725.6	724.5	723.5	722.5	723.5
160°	734.2	734.9	735.7	736.4	736.8	736.4	735.5	734.6	733.7	732.8	733.7
162.5°	742.8	743.7	744.6	745.5	745.9	745.5	744.8	744.0	743.3	742.5	743.3
165°	750.4	751.4	752.4	753.4	753.9	753.5	752.6	751.7	750.8	749.9	750.8
167.5°	756.6	757.6	758.7	759.7	760.2	759.7	758.7	757.6	756.6	755.6	756.6
170°	761.8	762.8	763.9	764.9	765.4	764.9	763.9	762.8	761.8	760.8	761.8
172.5°	765.2	766.2	767.3	768.3	768.8	768.2	767.1	765.9	764.8	763.6	764.8
175°	768.0	768.9	769.8	770.7	771.1	770.6	769.6	768.5	767.5	766.5	767.5
177.5°	769.2	770.2	771.3	772.3	772.8	772.2	770.9	769.6	768.4	767.1	768.4
180°	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4

TEST NUMBER: P1010950

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1
2.5°	962.1	957.5	954.5	952.2	949.9	956.8	947.6	937.7	930.8	926.2	924.7
5°	1062.8	1052.9	1044.5	1037.6	1039.2	1039.2	1023.1	1005.6	990.3	981.9	972.8
7.5°	1179.5	1168.9	1152.1	1148.3	1145.2	1126.1	1110.1	1078.1	1059.0	1039.9	1023.1
10°	1295.5	1281.8	1265.8	1260.4	1252.8	1229.1	1204.7	1163.5	1139.9	1104.8	1082.6
12.5°	1403.9	1387.1	1371.1	1367.2	1355.8	1335.2	1293.2	1250.5	1210.1	1172.7	1133.8
15°	1494.7	1490.1	1465.7	1450.4	1425.2	1397.0	1387.8	1329.9	1278.7	1239.8	1169.6
17.5°	1570.9	1549.6	1526.7	1516.8	1506.9	1474.1	1441.2	1381.7	1326.8	1269.6	1224.6
20°	1632.0	1608.3	1592.3	1577.8	1573.2	1535.9	1484.0	1431.3	1371.1	1307.0	1248.2
22.5°	1635.0	1632.0	1621.3	1612.9	1603.8	1579.3	1538.1	1472.5	1408.4	1338.2	1261.2
25°	1571.7	1567.1	1597.7	1590.0	1596.1	1587.0	1564.8	1509.9	1435.1	1352.7	1274.9
27.5°	1381.0	1427.5	1475.6	1492.4	1503.8	1536.6	1547.3	1516.8	1456.5	1368.8	1281.8
30°	1121.6	1183.4	1261.2	1303.1	1335.2	1396.2	1475.6	1485.5	1457.3	1387.1	1280.3
32.5°	880.5	936.9	999.5	1049.1	1091.8	1216.9	1323.7	1400.8	1414.5	1377.9	1284.1
35°	709.6	734.0	793.5	840.8	898.8	1005.6	1131.5	1255.8	1339.8	1344.3	1272.6
37.5°	585.2	598.2	650.0	676.8	711.1	804.9	922.4	1084.9	1215.4	1277.2	1240.6
40°	484.5	514.2	544.0	559.3	583.7	648.5	761.4	888.9	1050.6	1165.0	1191.0
42.5°	420.4	433.4	452.4	473.8	489.1	545.5	621.1	737.8	883.5	1043.0	1114.7
45°	370.8	375.4	395.2	409.0	425.0	464.6	518.1	615.7	743.9	901.1	1023.1
47.5°	329.6	338.8	349.4	357.8	368.5	399.0	444.8	515.8	628.7	769.1	900.3
50°	293.0	298.3	312.1	315.9	323.5	344.9	380.0	434.1	527.2	639.4	775.2
52.5°	258.6	268.6	273.9	279.2	286.1	303.7	326.5	370.8	441.0	546.3	661.5
55°	231.9	235.0	242.6	247.2	252.5	264.7	284.6	317.4	372.3	456.3	565.4
57.5°	206.0	206.0	213.6	217.4	222.8	231.9	249.5	274.7	314.3	376.9	476.9
60°	178.5	179.3	185.4	190.0	191.5	200.7	215.2	235.0	265.5	311.3	392.9
62.5°	154.1	157.9	161.0	162.5	167.9	173.2	185.4	199.1	220.5	260.9	318.9
65°	133.5	134.3	136.6	138.1	140.4	146.5	155.6	164.8	183.1	212.9	260.2
67.5°	109.9	112.9	116.0	116.0	118.3	121.3	130.5	138.1	151.8	169.4	201.4
70°	82.4	83.9	88.5	90.8	93.8	99.2	103.8	108.3	119.0	132.0	156.4
72.5°	68.7	68.7	70.2	71.0	71.0	74.8	81.6	86.2	91.6	100.7	117.5
75°	54.9	54.9	57.2	56.5	58.0	59.5	60.3	63.3	66.4	73.2	83.2
77.5°	43.5	44.3	44.3	45.0	45.0	45.8	46.5	48.1	49.6	53.4	58.0
80°	32.0	32.8	32.8	33.6	33.6	34.3	35.1	35.9	37.4	38.9	41.2
82.5°	22.1	22.9	22.9	23.7	22.9	23.7	24.4	24.4	25.2	26.7	27.5
85°	13.0	13.0	13.7	13.0	13.0	13.0	13.7	13.7	14.5	16.8	16.8
87.5°	3.8	4.6	3.8	4.6	4.6	4.6	4.6	5.3	5.3	6.1	6.9
90°	16.6	16.4	16.1	16.0	15.7	15.2	14.7	14.2	13.7	12.1	10.4
92.5°	19.2	19.1	19.0	18.9	18.5	17.6	16.7	15.8	14.9	13.7	12.6
95°	21.7	21.7	21.7	21.7	21.3	20.4	19.5	18.6	17.7	16.3	14.9
97.5°	23.2	23.1	23.0	22.9	22.4	21.4	20.3	19.3	18.3	24.8	31.2
100°	23.7	23.6	23.5	23.4	22.9	21.9	20.9	19.9	18.9	38.7	58.5
102.5°	24.1	23.8	23.5	23.4	25.5	29.7	33.9	38.1	42.3	64.4	86.5
105°	24.7	24.4	24.1	24.0	35.2	57.7	80.2	102.7	125.2	136.6	148.0
107.5°	92.7	109.3	126.0	134.3	144.1	163.6	183.2	202.7	222.3	220.4	218.5
110°	193.5	211.7	229.8	238.9	241.0	245.2	249.4	253.6	257.8	256.4	255.0

TEST NUMBER: P1010950

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	298.3	298.5	298.8	298.9	298.3	297.2	296.1	294.9	293.8	292.4	291.0
115°	335.1	334.6	334.1	333.8	333.2	331.9	330.6	329.4	328.1	326.9	325.8
117.5°	366.7	366.6	366.5	366.4	365.9	364.9	363.8	362.8	361.8	361.2	360.6
120°	399.0	399.0	399.0	399.0	398.5	397.5	396.4	395.4	394.4	394.0	393.6
122.5°	430.1	430.0	429.9	429.8	429.5	428.9	428.2	427.6	427.0	426.5	426.0
125°	459.1	458.8	458.5	458.4	458.3	458.0	457.8	457.5	457.3	456.8	456.3
127.5°	488.6	488.9	489.2	489.3	489.1	488.7	488.4	488.0	487.6	487.0	486.3
130°	516.1	516.3	516.6	516.7	516.4	515.9	515.4	514.9	514.4	513.9	513.4
132.5°	541.5	541.8	542.2	542.4	542.2	541.7	541.2	540.7	540.2	539.8	539.4
135°	567.2	567.6	568.0	568.2	568.0	567.6	567.2	566.8	566.4	565.9	565.4
137.5°	591.5	591.8	592.1	592.2	591.9	591.2	590.6	589.9	589.3	589.1	588.8
140°	613.2	613.5	613.8	613.9	613.6	613.1	612.6	612.1	611.6	611.2	610.8
142.5°	633.6	633.9	634.3	634.5	634.3	633.9	633.6	633.2	632.8	632.4	632.0
145°	653.3	653.3	653.3	653.3	653.2	652.9	652.7	652.4	652.2	651.9	651.7
147.5°	669.4	670.1	670.7	671.0	670.9	670.6	670.4	670.1	669.9	669.7	669.4
150°	686.1	686.5	686.9	687.1	687.0	686.7	686.4	686.2	685.9	685.7	685.4
152.5°	700.3	701.0	701.6	701.9	701.6	701.1	700.6	700.1	699.6	699.5	699.4
155°	713.2	713.9	714.7	715.1	714.8	714.1	713.5	712.8	712.2	712.1	711.9
157.5°	724.5	725.6	726.6	727.1	726.7	725.9	725.2	724.4	723.6	723.7	723.9
160°	734.6	735.5	736.4	736.8	736.4	735.7	734.9	734.2	733.4	733.5	733.6
162.5°	744.0	744.8	745.5	745.9	745.5	744.6	743.7	742.8	741.9	742.0	742.2
165°	751.7	752.6	753.5	753.9	753.4	752.4	751.4	750.4	749.4	749.5	749.6
167.5°	757.6	758.7	759.7	760.2	759.7	758.7	757.6	756.6	755.6	755.6	755.6
170°	762.8	763.9	764.9	765.4	764.9	763.9	762.8	761.8	760.8	760.8	760.8
172.5°	765.9	767.1	768.2	768.8	768.3	767.3	766.2	765.2	764.2	764.1	763.9
175°	768.5	769.6	770.6	771.1	770.7	769.8	768.9	768.0	767.1	767.0	766.8
177.5°	769.6	770.9	772.2	772.8	772.3	771.3	770.2	769.2	768.2	768.1	767.9
180°	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4

TEST NUMBER: P1010950

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1
2.5°	922.4	918.6	914.8	914.8	906.4	898.8	895.0	896.5	891.9	885.8	879.7
5°	962.9	947.6	944.6	936.2	924.7	908.7	900.3	892.7	883.5	871.3	859.9
7.5°	1000.2	980.4	969.7	961.3	939.2	917.1	898.8	886.6	870.5	852.2	838.5
10°	1049.1	1012.5	1001.0	981.9	950.7	919.4	898.0	878.2	856.0	834.7	816.4
12.5°	1088.0	1046.0	1024.7	1005.6	965.2	925.5	889.6	865.2	838.5	814.8	791.2
15°	1132.2	1084.9	1047.6	1024.7	973.5	925.5	885.0	850.7	821.0	792.0	771.4
17.5°	1153.6	1094.1	1077.3	1044.5	970.5	922.4	872.8	836.2	800.4	766.8	742.4
20°	1187.2	1117.7	1075.8	1053.7	988.0	917.1	859.1	817.1	779.8	743.9	718.0
22.5°	1189.5	1113.9	1086.5	1044.5	963.6	901.1	846.9	795.8	752.3	718.7	692.0
25°	1184.1	1107.1	1068.9	1035.3	968.2	891.9	822.5	772.1	729.4	690.5	659.2
27.5°	1181.8	1087.2	1051.4	1017.8	942.3	865.2	808.0	750.8	701.9	667.6	635.6
30°	1178.8	1065.9	1022.4	983.5	914.0	844.6	775.9	726.3	679.8	636.3	604.3
32.5°	1158.9	1036.9	992.6	951.4	876.6	807.2	753.0	700.4	650.0	609.6	580.6
35°	1152.8	1010.2	952.2	907.9	834.7	772.9	715.7	672.2	624.9	584.4	550.1
37.5°	1135.3	982.7	920.1	863.7	787.4	728.6	686.7	643.2	597.4	553.9	526.4
40°	1104.8	950.7	879.7	821.7	743.1	683.6	644.7	612.7	567.6	528.7	495.2
42.5°	1059.8	917.8	841.6	780.5	693.5	637.8	605.8	575.3	537.1	496.7	469.2
45°	1007.9	874.4	803.4	735.5	647.0	592.8	559.3	540.9	505.8	471.5	439.5
47.5°	936.9	829.3	759.2	689.0	598.9	546.3	519.6	501.3	476.9	439.5	413.5
50°	847.7	771.4	705.0	642.4	551.6	501.3	474.6	460.8	440.2	413.5	388.3
52.5°	748.5	704.2	649.3	591.3	503.6	456.3	431.8	421.2	405.9	380.7	359.4
55°	648.5	629.4	592.1	534.8	453.2	414.3	392.9	379.2	367.7	349.4	331.1
57.5°	559.3	550.1	524.2	479.9	411.2	370.8	352.5	343.3	334.2	320.4	302.1
60°	466.9	476.9	450.2	428.0	365.5	330.4	314.3	304.4	299.8	287.6	276.2
62.5°	386.8	396.0	380.7	363.9	319.7	288.4	278.5	269.3	266.3	255.6	244.1
65°	314.3	325.8	314.3	305.2	278.5	252.5	240.3	235.8	232.7	225.8	216.7
67.5°	250.3	261.7	256.4	244.9	236.5	215.2	208.3	203.7	202.2	196.8	189.2
70°	188.5	204.5	206.0	199.1	191.5	181.6	177.0	175.5	171.7	167.1	162.5
72.5°	135.8	154.1	154.9	154.9	150.3	150.3	145.7	143.4	143.4	138.9	133.5
75°	99.9	112.2	113.7	115.2	117.5	119.8	116.7	116.7	116.0	111.4	109.1
77.5°	66.4	77.1	80.9	86.2	89.3	89.3	90.8	92.3	90.8	88.5	87.0
80°	42.7	50.4	54.9	58.0	62.6	64.9	67.1	67.9	66.4	65.6	63.3
82.5°	28.2	30.5	32.8	36.6	42.0	45.8	45.8	45.0	46.5	45.8	45.0
85°	16.0	17.5	18.3	19.1	22.1	25.9	26.7	27.5	29.0	27.5	25.9
87.5°	6.1	6.9	6.9	6.9	8.4	9.2	11.4	14.5	13.7	12.2	12.2
90°	8.8	7.1	6.3	5.7	4.4	3.1	1.9	0.6	1.9	3.1	4.4
92.5°	11.4	10.3	9.7	10.1	10.8	11.6	12.3	13.1	12.3	11.6	10.8
95°	13.5	12.1	11.4	14.0	19.2	24.5	29.7	34.9	29.7	24.5	19.2
97.5°	37.7	44.2	47.4	49.2	52.7	56.3	59.8	63.4	59.8	56.3	52.7
100°	78.3	98.1	108.0	106.7	104.2	101.7	99.1	96.6	99.1	101.7	104.2
102.5°	108.6	130.7	141.8	141.0	139.3	137.6	136.0	134.3	136.0	137.6	139.3
105°	159.5	170.9	176.6	175.9	174.5	173.1	171.7	170.3	171.7	173.1	174.5
107.5°	216.6	214.7	213.8	213.2	212.1	210.9	209.8	208.6	209.8	210.9	212.1
110°	253.6	252.2	251.5	251.0	250.0	248.9	247.9	246.9	247.9	248.9	250.0

TEST NUMBER: P1010950

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	289.6	288.2	287.5	287.1	286.2	285.3	284.4	283.5	284.4	285.3	286.2
115°	324.6	323.5	322.9	322.5	321.8	321.0	320.3	319.5	320.3	321.0	321.8
117.5°	359.9	359.3	359.0	358.6	357.7	356.8	355.9	355.0	355.9	356.8	357.7
120°	393.3	392.9	392.7	392.1	391.0	389.8	388.7	387.5	388.7	389.8	391.0
122.5°	425.5	425.0	424.7	424.3	423.4	422.5	421.6	420.7	421.6	422.5	423.4
125°	455.8	455.3	455.0	454.5	453.5	452.4	451.4	450.4	451.4	452.4	453.5
127.5°	485.7	485.0	484.7	484.2	483.2	482.1	481.1	480.1	481.1	482.1	483.2
130°	512.9	512.4	512.1	511.6	510.6	509.6	508.6	507.6	508.6	509.6	510.6
132.5°	539.0	538.6	538.4	537.9	536.9	535.9	534.9	533.9	534.9	535.9	536.9
135°	564.9	564.4	564.2	563.8	563.0	562.3	561.5	560.7	561.5	562.3	563.0
137.5°	588.6	588.3	588.2	587.7	586.7	585.6	584.6	583.6	584.6	585.6	586.7
140°	610.5	610.1	609.9	609.5	608.8	608.0	607.3	606.5	607.3	608.0	608.8
142.5°	631.6	631.2	631.0	630.6	629.9	629.1	628.4	627.6	628.4	629.1	629.9
145°	651.4	651.1	651.0	650.6	649.7	648.8	647.9	647.0	647.9	648.8	649.7
147.5°	669.2	668.9	668.8	668.5	667.8	667.2	666.5	665.9	666.5	667.2	667.8
150°	685.2	684.9	684.8	684.6	684.2	683.9	683.5	683.1	683.5	683.9	684.2
152.5°	699.3	699.2	699.1	699.0	698.9	698.8	698.6	698.5	698.6	698.8	698.9
155°	711.8	711.7	711.6	711.7	712.0	712.3	712.5	712.8	712.5	712.3	712.0
157.5°	724.0	724.1	724.2	724.2	724.2	724.2	724.2	724.2	724.2	724.2	724.2
160°	733.7	733.8	733.9	734.0	734.1	734.2	734.4	734.5	734.4	734.2	734.1
162.5°	742.3	742.4	742.5	742.7	743.1	743.4	743.8	744.2	743.8	743.4	743.1
165°	749.7	749.8	749.9	750.1	750.5	750.8	751.2	751.6	751.2	750.8	750.5
167.5°	755.6	755.6	755.6	755.9	756.4	756.9	757.4	757.9	757.4	756.9	756.4
170°	760.8	760.8	760.8	761.1	761.6	762.1	762.6	763.1	762.6	762.1	761.6
172.5°	763.8	763.7	763.6	763.9	764.6	765.2	765.9	766.5	765.9	765.2	764.6
175°	766.7	766.6	766.5	766.8	767.5	768.1	768.8	769.4	768.8	768.1	767.5
177.5°	767.8	767.7	767.6	767.9	768.6	769.2	769.9	770.5	769.9	769.2	768.6
180°	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4

TEST NUMBER: P1010950

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1
2.5°	879.7	875.9	874.4	870.5	861.4	855.3	848.4	843.8	844.6	840.8	843.1
5°	852.2	851.5	846.1	838.5	825.5	818.7	806.5	800.4	797.3	798.1	793.5
7.5°	829.3	822.5	818.7	806.5	794.2	779.8	769.8	764.5	759.9	755.3	752.3
10°	803.4	797.3	791.2	778.2	761.4	747.7	734.0	728.6	721.8	718.7	716.4
12.5°	775.9	772.1	764.5	749.2	730.2	717.2	701.2	698.1	689.0	682.9	681.3
15°	750.8	748.5	734.7	717.2	698.1	685.1	671.4	662.3	647.0	650.0	644.7
17.5°	724.1	714.1	705.7	682.1	672.9	653.1	637.1	632.5	621.8	615.0	608.1
20°	694.3	688.2	677.5	662.3	640.1	617.2	605.0	597.4	591.3	580.6	577.6
22.5°	666.1	658.4	649.3	629.4	610.4	591.3	574.5	567.6	560.0	552.4	547.8
25°	643.9	632.5	622.6	598.2	579.1	563.1	552.4	540.9	530.3	525.7	524.2
27.5°	609.6	602.7	592.8	569.9	552.4	534.8	524.9	517.3	505.8	500.5	495.9
30°	587.5	573.8	562.3	544.0	526.4	507.4	498.2	489.1	482.2	475.3	470.0
32.5°	557.7	547.0	537.9	519.6	502.0	484.5	474.6	460.8	457.0	451.7	445.6
35°	528.7	521.9	512.0	492.1	473.0	460.8	450.2	437.2	432.6	428.8	423.4
37.5°	501.3	491.4	484.5	465.4	448.6	434.1	425.7	415.1	412.0	407.4	403.6
40°	477.6	467.7	460.8	441.8	424.2	409.0	403.6	392.9	388.3	383.0	380.7
42.5°	450.9	442.5	433.4	419.6	401.3	386.1	375.4	369.3	363.2	360.9	356.3
45°	422.7	415.1	408.2	392.9	373.9	363.2	354.0	345.6	341.0	337.2	334.2
47.5°	398.3	391.4	382.2	365.5	350.2	340.3	331.1	322.7	318.2	313.6	309.8
50°	370.0	366.2	356.3	340.3	325.8	314.3	305.9	298.3	295.3	289.9	283.8
52.5°	344.9	338.0	329.6	316.6	303.7	289.9	278.5	273.9	268.6	265.5	260.2
55°	315.1	310.5	301.4	289.9	276.2	264.7	256.4	250.3	243.4	240.3	233.5
57.5°	289.9	281.5	277.0	262.5	249.5	238.0	231.9	225.8	218.2	213.6	210.6
60°	262.5	254.8	248.0	235.8	226.6	214.4	205.2	199.9	194.6	188.5	185.4
62.5°	235.8	229.7	221.3	211.3	199.9	190.0	183.1	175.5	172.4	166.3	164.0
65°	206.8	202.2	195.3	183.9	174.7	166.3	159.5	153.4	150.3	148.0	146.5
67.5°	180.8	174.7	170.1	160.2	150.3	143.4	139.6	135.8	132.0	129.7	127.4
70°	154.1	149.5	145.0	135.8	128.9	122.8	119.8	116.7	114.4	112.2	109.9
72.5°	126.7	124.4	119.8	113.7	108.3	103.8	101.5	97.7	95.4	91.6	90.0
75°	104.5	100.7	98.4	93.1	88.5	84.7	81.6	77.1	74.0	72.5	71.7
77.5°	82.4	80.9	77.8	73.2	71.0	67.1	62.6	61.0	59.5	59.5	58.7
80°	61.8	59.5	57.2	53.4	51.1	48.1	48.1	48.1	47.3	48.1	47.3
82.5°	42.0	40.4	38.9	36.6	35.9	35.9	36.6	36.6	36.6	36.6	36.6
85°	24.4	24.4	24.4	25.2	24.4	24.4	25.2	25.9	25.2	25.2	24.4
87.5°	11.4	11.4	12.2	12.2	13.0	13.0	13.0	13.0	13.0	13.0	13.7
90°	5.7	6.3	7.1	8.8	10.4	12.1	13.7	14.2	14.7	15.2	15.7
92.5°	10.1	9.7	10.3	11.4	12.6	13.7	14.9	15.8	16.7	17.6	18.5
95°	14.0	11.4	12.1	13.5	14.9	16.3	17.7	18.6	19.5	20.4	21.3
97.5°	49.2	47.4	44.2	37.7	31.2	24.8	18.3	19.3	20.3	21.4	22.4
100°	106.7	108.0	98.1	78.3	58.5	38.7	18.9	19.9	20.9	21.9	22.9
102.5°	141.0	141.8	130.7	108.6	86.5	64.4	42.3	38.1	33.9	29.7	25.5
105°	175.9	176.6	170.9	159.5	148.0	136.6	125.2	102.7	80.2	57.7	35.2
107.5°	213.2	213.8	214.7	216.6	218.5	220.4	222.3	202.7	183.2	163.6	144.1
110°	251.0	251.5	252.2	253.6	255.0	256.4	257.8	253.6	249.4	245.2	241.0

TEST NUMBER: P1010950

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	287.1	287.5	288.2	289.6	291.0	292.4	293.8	294.9	296.1	297.2	298.3
115°	322.5	322.9	323.5	324.6	325.8	326.9	328.1	329.4	330.6	331.9	333.2
117.5°	358.6	359.0	359.3	359.9	360.6	361.2	361.8	362.8	363.8	364.9	365.9
120°	392.1	392.7	392.9	393.3	393.6	394.0	394.4	395.4	396.4	397.5	398.5
122.5°	424.3	424.7	425.0	425.5	426.0	426.5	427.0	427.6	428.2	428.9	429.5
125°	454.5	455.0	455.3	455.8	456.3	456.8	457.3	457.5	457.8	458.0	458.3
127.5°	484.2	484.7	485.0	485.7	486.3	487.0	487.6	488.0	488.4	488.7	489.1
130°	511.6	512.1	512.4	512.9	513.4	513.9	514.4	514.9	515.4	515.9	516.4
132.5°	537.9	538.4	538.6	539.0	539.4	539.8	540.2	540.7	541.2	541.7	542.2
135°	563.8	564.2	564.4	564.9	565.4	565.9	566.4	566.8	567.2	567.6	568.0
137.5°	587.7	588.2	588.3	588.6	588.8	589.1	589.3	589.9	590.6	591.2	591.9
140°	609.5	609.9	610.1	610.5	610.8	611.2	611.6	612.1	612.6	613.1	613.6
142.5°	630.6	631.0	631.2	631.6	632.0	632.4	632.8	633.2	633.6	633.9	634.3
145°	650.6	651.0	651.1	651.4	651.7	651.9	652.2	652.4	652.7	652.9	653.2
147.5°	668.5	668.8	668.9	669.2	669.4	669.7	669.9	670.1	670.4	670.6	670.9
150°	684.6	684.8	684.9	685.2	685.4	685.7	685.9	686.2	686.4	686.7	687.0
152.5°	699.0	699.1	699.2	699.3	699.4	699.5	699.6	700.1	700.6	701.1	701.6
155°	711.7	711.6	711.7	711.8	711.9	712.1	712.2	712.8	713.5	714.1	714.8
157.5°	724.2	724.2	724.1	724.0	723.9	723.7	723.6	724.4	725.2	725.9	726.7
160°	734.0	733.9	733.8	733.7	733.6	733.5	733.4	734.2	734.9	735.7	736.4
162.5°	742.7	742.5	742.4	742.3	742.2	742.0	741.9	742.8	743.7	744.6	745.5
165°	750.1	749.9	749.8	749.7	749.6	749.5	749.4	750.4	751.4	752.4	753.4
167.5°	755.9	755.6	755.6	755.6	755.6	755.6	755.6	756.6	757.6	758.7	759.7
170°	761.1	760.8	760.8	760.8	760.8	760.8	760.8	761.8	762.8	763.9	764.9
172.5°	763.9	763.6	763.7	763.8	763.9	764.1	764.2	765.2	766.2	767.3	768.3
175°	766.8	766.5	766.6	766.7	766.8	767.0	767.1	768.0	768.9	769.8	770.7
177.5°	767.9	767.6	767.7	767.8	767.9	768.1	768.2	769.2	770.2	771.3	772.3
180°	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4

TEST NUMBER: P1010950

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1
2.5°	842.3	843.1	840.8	836.2	835.4	837.0	841.6	840.0	836.2	843.1	837.0
5°	795.8	792.0	790.4	792.0	787.4	785.1	789.7	787.4	789.7	790.4	792.7
7.5°	750.8	751.5	746.9	747.7	741.6	743.1	743.1	743.1	745.4	746.9	750.0
10°	711.8	713.4	708.0	708.8	704.2	701.2	703.5	708.0	708.0	708.0	709.6
12.5°	680.6	673.7	669.9	669.1	663.8	662.3	666.8	668.4	672.2	672.2	674.5
15°	641.7	640.1	637.1	637.1	624.1	627.2	628.7	634.0	641.7	635.6	637.1
17.5°	606.6	602.7	598.9	597.4	595.9	591.3	597.4	596.6	601.2	602.0	604.3
20°	575.3	572.2	564.6	565.4	566.9	560.0	563.8	563.8	568.4	573.0	578.3
22.5°	544.8	541.7	537.9	539.4	534.8	533.3	533.3	537.1	542.5	546.3	545.5
25°	521.1	515.8	513.5	511.2	508.9	510.4	508.1	512.0	515.8	518.1	515.8
27.5°	494.4	492.1	487.5	485.2	481.4	483.0	484.5	487.5	489.8	489.8	492.1
30°	468.5	465.4	463.9	461.6	461.6	458.5	459.3	462.4	464.6	466.9	470.0
32.5°	443.3	441.0	438.7	438.7	437.2	436.4	435.7	440.2	440.2	444.8	444.8
35°	422.7	418.9	418.9	415.1	416.6	415.8	414.3	417.3	418.1	421.2	420.4
37.5°	399.8	399.8	398.3	394.5	391.4	392.2	396.0	396.0	398.3	397.5	399.8
40°	376.9	375.4	375.4	373.1	372.3	371.6	372.3	373.1	376.9	376.1	376.9
42.5°	354.0	354.8	351.0	351.0	351.0	348.7	349.4	350.2	351.7	353.3	355.5
45°	331.9	330.4	329.6	328.1	326.5	327.3	326.5	329.6	328.8	330.4	332.7
47.5°	308.2	305.9	305.2	302.1	302.1	303.7	302.9	305.2	305.9	308.2	306.7
50°	285.3	282.3	280.0	280.8	276.2	277.7	277.7	280.0	282.3	283.1	284.6
52.5°	258.6	257.9	257.1	253.3	252.5	251.8	252.5	253.3	256.4	258.6	259.4
55°	232.7	231.9	227.4	225.8	223.5	223.5	225.1	225.8	231.2	231.9	235.0
57.5°	209.1	206.8	201.4	200.7	200.7	200.7	198.4	201.4	202.9	206.8	206.8
60°	183.1	183.1	178.5	178.5	179.3	178.5	178.5	179.3	179.3	182.3	183.9
62.5°	162.5	161.7	161.7	160.2	159.5	160.2	159.5	159.5	160.2	162.5	164.8
65°	144.2	143.4	142.7	141.9	140.4	140.4	141.1	142.7	142.7	144.2	145.0
67.5°	126.7	126.7	125.1	125.1	124.4	123.6	124.4	123.6	126.7	126.7	127.4
70°	109.1	108.3	106.1	105.3	103.0	103.8	103.8	106.1	106.8	108.3	109.9
72.5°	87.7	87.7	86.2	84.7	85.5	83.9	83.9	84.7	84.7	87.0	87.7
75°	72.5	71.0	70.2	71.0	70.2	71.7	70.2	70.2	71.7	71.7	71.7
77.5°	59.5	59.5	58.7	58.7	59.5	58.7	59.5	59.5	59.5	58.7	59.5
80°	48.8	48.1	48.1	48.1	47.3	47.3	47.3	47.3	47.3	47.3	47.3
82.5°	36.6	36.6	35.9	36.6	36.6	35.9	36.6	35.9	35.9	36.6	36.6
85°	24.4	25.9	24.4	24.4	25.2	25.2	25.9	25.2	25.9	24.4	25.2
87.5°	13.0	13.7	13.7	13.0	13.0	13.7	13.7	13.7	14.5	13.0	13.7
90°	16.0	16.1	16.4	16.6	16.9	17.1	16.9	16.6	16.4	16.1	16.0
92.5°	18.9	19.0	19.1	19.2	19.3	19.4	19.3	19.2	19.1	19.0	18.9
95°	21.7	21.7	21.7	21.7	21.7	21.7	21.7	21.7	21.7	21.7	21.7
97.5°	22.9	23.0	23.1	23.2	23.3	23.4	23.3	23.2	23.1	23.0	22.9
100°	23.4	23.5	23.6	23.7	23.9	24.0	23.9	23.7	23.6	23.5	23.4
102.5°	23.4	23.5	23.8	24.1	24.3	24.6	24.3	24.1	23.8	23.5	23.4
105°	24.0	24.1	24.4	24.7	24.9	25.2	24.9	24.7	24.4	24.1	24.0
107.5°	134.3	126.0	109.3	92.7	76.0	59.4	76.0	92.7	109.3	126.0	134.3
110°	238.9	229.8	211.7	193.5	175.4	157.2	175.4	193.5	211.7	229.8	238.9



TEST NUMBER: P1010950

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	298.9	298.8	298.5	298.3	298.0	297.8	298.0	298.3	298.5	298.8	298.9
115°	333.8	334.1	334.6	335.1	335.6	336.1	335.6	335.1	334.6	334.1	333.8
117.5°	366.4	366.5	366.6	366.7	366.9	367.0	366.9	366.7	366.6	366.5	366.4
120°	399.0	399.0	399.0	399.0	399.0	399.0	399.0	399.0	399.0	399.0	399.0
122.5°	429.8	429.9	430.0	430.1	430.3	430.4	430.3	430.1	430.0	429.9	429.8
125°	458.4	458.5	458.8	459.1	459.3	459.6	459.3	459.1	458.8	458.5	458.4
127.5°	489.3	489.2	488.9	488.6	488.4	488.1	488.4	488.6	488.9	489.2	489.3
130°	516.7	516.6	516.3	516.1	515.8	515.6	515.8	516.1	516.3	516.6	516.7
132.5°	542.4	542.2	541.8	541.5	541.1	540.7	541.1	541.5	541.8	542.2	542.4
135°	568.2	568.0	567.6	567.2	566.8	566.4	566.8	567.2	567.6	568.0	568.2
137.5°	592.2	592.1	591.8	591.5	591.3	591.0	591.3	591.5	591.8	592.1	592.2
140°	613.9	613.8	613.5	613.2	613.0	612.7	613.0	613.2	613.5	613.8	613.9
142.5°	634.5	634.3	633.9	633.6	633.2	632.8	633.2	633.6	633.9	634.3	634.5
145°	653.3	653.3	653.3	653.3	653.3	653.3	653.3	653.3	653.3	653.3	653.3
147.5°	671.0	670.7	670.1	669.4	668.8	668.2	668.8	669.4	670.1	670.7	671.0
150°	687.1	686.9	686.5	686.1	685.7	685.3	685.7	686.1	686.5	686.9	687.1
152.5°	701.9	701.6	701.0	700.3	699.7	699.1	699.7	700.3	701.0	701.6	701.9
155°	715.1	714.7	713.9	713.2	712.4	711.6	712.4	713.2	713.9	714.7	715.1
157.5°	727.1	726.6	725.6	724.5	723.5	722.5	723.5	724.5	725.6	726.6	727.1
160°	736.8	736.4	735.5	734.6	733.7	732.8	733.7	734.6	735.5	736.4	736.8
162.5°	745.9	745.5	744.8	744.0	743.3	742.5	743.3	744.0	744.8	745.5	745.9
165°	753.9	753.5	752.6	751.7	750.8	749.9	750.8	751.7	752.6	753.5	753.9
167.5°	760.2	759.7	758.7	757.6	756.6	755.6	756.6	757.6	758.7	759.7	760.2
170°	765.4	764.9	763.9	762.8	761.8	760.8	761.8	762.8	763.9	764.9	765.4
172.5°	768.8	768.2	767.1	765.9	764.8	763.6	764.8	765.9	767.1	768.2	768.8
175°	771.1	770.6	769.6	768.5	767.5	766.5	767.5	768.5	769.6	770.6	771.1
177.5°	772.8	772.2	770.9	769.6	768.4	767.1	768.4	769.6	770.9	772.2	772.8
180°	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4

TEST NUMBER: P1010950

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1	891.1
2.5°	843.1	846.1	843.1	837.0	843.1	846.9	850.7	856.8	859.9	859.9	864.4
5°	795.0	801.1	798.8	797.3	803.4	807.2	813.3	821.0	829.3	834.7	840.8
7.5°	752.3	756.1	759.9	759.9	766.0	774.4	783.6	792.7	803.4	811.0	815.6
10°	714.9	718.0	720.2	723.3	732.4	741.6	753.8	765.3	774.4	782.8	790.4
12.5°	679.0	683.6	689.0	691.2	698.1	709.6	721.0	734.7	749.2	757.6	765.3
15°	644.7	647.0	653.1	660.0	666.1	678.3	692.8	707.3	719.5	732.4	739.3
17.5°	609.6	610.4	626.4	622.6	642.4	653.9	661.5	675.2	695.1	705.7	716.4
20°	575.3	582.9	589.8	593.6	604.3	617.2	639.4	650.0	666.1	676.0	685.1
22.5°	548.6	560.0	560.0	569.2	574.5	586.7	602.7	623.3	640.9	647.8	660.7
25°	524.9	530.3	539.4	542.5	552.4	563.1	573.8	595.9	615.0	624.1	633.3
27.5°	494.4	501.3	513.5	513.5	526.4	537.9	550.9	565.4	584.4	597.4	607.3
30°	470.8	477.6	483.0	491.4	496.7	507.4	530.3	540.9	557.7	569.2	581.4
32.5°	448.6	454.0	458.5	467.7	473.8	486.0	498.2	517.3	531.8	542.5	555.4
35°	424.2	429.6	435.7	442.5	451.7	463.1	474.6	490.6	505.1	515.0	525.7
37.5°	401.3	405.1	414.3	418.9	426.5	437.2	451.7	468.5	481.4	489.1	499.7
40°	379.2	382.2	389.1	397.5	402.8	411.2	426.5	441.0	457.0	466.2	474.6
42.5°	355.5	359.4	365.5	373.9	382.2	391.4	399.8	416.6	431.1	438.7	447.9
45°	334.9	337.2	341.8	350.2	358.6	365.5	378.4	393.7	407.4	413.5	423.4
47.5°	310.5	312.8	319.7	323.5	332.7	341.8	354.8	370.0	382.2	388.3	397.5
50°	285.3	287.6	292.2	300.6	306.7	316.6	328.1	341.0	356.3	364.7	370.0
52.5°	260.9	265.5	269.3	276.2	283.8	293.7	304.4	316.6	329.6	338.0	344.1
55°	236.5	240.3	244.9	248.7	257.9	267.0	279.2	290.7	302.1	309.8	316.6
57.5°	209.1	214.4	219.0	226.6	233.5	241.1	254.8	264.0	277.7	283.1	289.2
60°	185.4	190.7	194.6	200.7	206.8	216.7	225.8	237.3	248.7	255.6	263.2
62.5°	165.6	167.9	170.1	176.2	182.3	191.5	200.7	212.1	224.3	228.1	234.2
65°	145.7	148.0	151.8	157.2	161.7	167.1	177.0	186.2	197.6	203.7	206.0
67.5°	128.9	131.2	132.0	135.8	139.6	145.7	151.1	160.2	170.9	174.7	179.3
70°	109.9	113.7	114.4	117.5	119.0	122.8	128.9	135.8	144.2	151.1	154.9
72.5°	87.7	93.1	94.6	99.2	101.5	105.3	109.9	115.2	120.5	123.6	126.7
75°	71.7	73.2	74.0	77.8	81.6	87.0	89.3	92.3	96.9	100.7	103.8
77.5°	59.5	60.3	61.0	61.0	61.8	64.9	69.4	73.2	76.3	77.8	80.1
80°	48.1	47.3	47.3	48.1	48.1	48.1	49.6	54.9	56.5	60.3	59.5
82.5°	37.4	35.9	36.6	35.9	35.9	35.9	35.9	36.6	36.6	38.9	40.4
85°	24.4	25.2	24.4	24.4	23.7	24.4	23.7	23.7	22.9	22.9	22.1
87.5°	13.0	13.7	13.0	13.0	12.2	13.0	12.2	12.2	11.4	11.4	9.9
90°	15.7	15.2	14.7	14.2	13.7	12.1	10.4	8.8	7.1	6.3	5.7
92.5°	18.5	17.6	16.7	15.8	14.9	13.7	12.6	11.4	10.3	9.7	10.1
95°	21.3	20.4	19.5	18.6	17.7	16.3	14.9	13.5	12.1	11.4	14.0
97.5°	22.4	21.4	20.3	19.3	18.3	24.8	31.2	37.7	44.2	47.4	49.2
100°	22.9	21.9	20.9	19.9	18.9	38.7	58.5	78.3	98.1	108.0	106.7
102.5°	25.5	29.7	33.9	38.1	42.3	64.4	86.5	108.6	130.7	141.8	141.0
105°	35.2	57.7	80.2	102.7	125.2	136.6	148.0	159.5	170.9	176.6	175.9
107.5°	144.1	163.6	183.2	202.7	222.3	220.4	218.5	216.6	214.7	213.8	213.2
110°	241.0	245.2	249.4	253.6	257.8	256.4	255.0	253.6	252.2	251.5	251.0

TEST NUMBER: P1010950

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	298.3	297.2	296.1	294.9	293.8	292.4	291.0	289.6	288.2	287.5	287.1
115°	333.2	331.9	330.6	329.4	328.1	326.9	325.8	324.6	323.5	322.9	322.5
117.5°	365.9	364.9	363.8	362.8	361.8	361.2	360.6	359.9	359.3	359.0	358.6
120°	398.5	397.5	396.4	395.4	394.4	394.0	393.6	393.3	392.9	392.7	392.1
122.5°	429.5	428.9	428.2	427.6	427.0	426.5	426.0	425.5	425.0	424.7	424.3
125°	458.3	458.0	457.8	457.5	457.3	456.8	456.3	455.8	455.3	455.0	454.5
127.5°	489.1	488.7	488.4	488.0	487.6	487.0	486.3	485.7	485.0	484.7	484.2
130°	516.4	515.9	515.4	514.9	514.4	513.9	513.4	512.9	512.4	512.1	511.6
132.5°	542.2	541.7	541.2	540.7	540.2	539.8	539.4	539.0	538.6	538.4	537.9
135°	568.0	567.6	567.2	566.8	566.4	565.9	565.4	564.9	564.4	564.2	563.8
137.5°	591.9	591.2	590.6	589.9	589.3	589.1	588.8	588.6	588.3	588.2	587.7
140°	613.6	613.1	612.6	612.1	611.6	611.2	610.8	610.5	610.1	609.9	609.5
142.5°	634.3	633.9	633.6	633.2	632.8	632.4	632.0	631.6	631.2	631.0	630.6
145°	653.2	652.9	652.7	652.4	652.2	651.9	651.7	651.4	651.1	651.0	650.6
147.5°	670.9	670.6	670.4	670.1	669.9	669.7	669.4	669.2	668.9	668.8	668.5
150°	687.0	686.7	686.4	686.2	685.9	685.7	685.4	685.2	684.9	684.8	684.6
152.5°	701.6	701.1	700.6	700.1	699.6	699.5	699.4	699.3	699.2	699.1	699.0
155°	714.8	714.1	713.5	712.8	712.2	712.1	711.9	711.8	711.7	711.6	711.7
157.5°	726.7	725.9	725.2	724.4	723.6	723.7	723.9	724.0	724.1	724.2	724.2
160°	736.4	735.7	734.9	734.2	733.4	733.5	733.6	733.7	733.8	733.9	734.0
162.5°	745.5	744.6	743.7	742.8	741.9	742.0	742.2	742.3	742.4	742.5	742.7
165°	753.4	752.4	751.4	750.4	749.4	749.5	749.6	749.7	749.8	749.9	750.1
167.5°	759.7	758.7	757.6	756.6	755.6	755.6	755.6	755.6	755.6	755.6	755.9
170°	764.9	763.9	762.8	761.8	760.8	760.8	760.8	760.8	760.8	760.8	761.1
172.5°	768.3	767.3	766.2	765.2	764.2	764.1	763.9	763.8	763.7	763.6	763.9
175°	770.7	769.8	768.9	768.0	767.1	767.0	766.8	766.7	766.6	766.5	766.8
177.5°	772.3	771.3	770.2	769.2	768.2	768.1	767.9	767.8	767.7	767.6	767.9
180°	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4

TEST NUMBER: P1010950

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	891.1	891.1	891.1	891.1
2.5°	868.3	873.6	884.3	893.4
5°	849.9	858.3	874.4	890.4
7.5°	827.8	840.8	861.4	883.5
10°	806.5	823.2	848.4	874.4
12.5°	785.1	802.6	829.3	862.9
15°	759.9	778.2	810.3	850.7
17.5°	737.8	762.2	791.2	831.6
20°	714.1	732.4	769.8	812.6
22.5°	684.4	714.9	750.0	795.0
25°	660.7	687.4	722.5	773.6
27.5°	631.7	663.0	705.7	750.8
30°	608.1	634.0	673.7	727.9
32.5°	580.6	611.1	652.3	705.7
35°	556.2	582.1	621.1	675.2
37.5°	527.2	555.4	598.9	647.0
40°	502.0	529.5	570.7	615.7
42.5°	471.5	500.5	541.7	579.9
45°	447.1	473.8	506.6	541.7
47.5°	417.3	445.6	477.6	502.0
50°	390.6	416.6	441.8	462.4
52.5°	361.6	385.3	408.2	423.4
55°	334.9	353.3	371.6	382.2
57.5°	303.7	321.2	336.5	342.6
60°	276.2	290.7	300.6	307.5
62.5°	247.2	257.9	265.5	269.3
65°	219.0	226.6	230.4	234.2
67.5°	190.0	196.8	199.1	203.7
70°	159.5	167.1	168.6	170.9
72.5°	136.6	136.6	139.6	142.7
75°	109.1	110.6	112.2	112.2
77.5°	85.5	85.5	87.0	87.7
80°	62.6	63.3	63.3	62.6
82.5°	42.7	44.3	42.7	42.0
85°	23.7	26.7	25.2	25.2
87.5°	9.9	9.9	11.4	9.9
90°	4.4	3.1	1.9	0.6
92.5°	10.8	11.6	12.3	13.1
95°	19.2	24.5	29.7	34.9
97.5°	52.7	56.3	59.8	63.4
100°	104.2	101.7	99.1	96.6
102.5°	139.3	137.6	136.0	134.3
105°	174.5	173.1	171.7	170.3
107.5°	212.1	210.9	209.8	208.6
110°	250.0	248.9	247.9	246.9

TEST NUMBER: P1010950

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	286.2	285.3	284.4	283.5
115°	321.8	321.0	320.3	319.5
117.5°	357.7	356.8	355.9	355.0
120°	391.0	389.8	388.7	387.5
122.5°	423.4	422.5	421.6	420.7
125°	453.5	452.4	451.4	450.4
127.5°	483.2	482.1	481.1	480.1
130°	510.6	509.6	508.6	507.6
132.5°	536.9	535.9	534.9	533.9
135°	563.0	562.3	561.5	560.7
137.5°	586.7	585.6	584.6	583.6
140°	608.8	608.0	607.3	606.5
142.5°	629.9	629.1	628.4	627.6
145°	649.7	648.8	647.9	647.0
147.5°	667.8	667.2	666.5	665.9
150°	684.2	683.9	683.5	683.1
152.5°	698.9	698.8	698.6	698.5
155°	712.0	712.3	712.5	712.8
157.5°	724.2	724.2	724.2	724.2
160°	734.1	734.2	734.4	734.5
162.5°	743.1	743.4	743.8	744.2
165°	750.5	750.8	751.2	751.6
167.5°	756.4	756.9	757.4	757.9
170°	761.6	762.1	762.6	763.1
172.5°	764.6	765.2	765.9	766.5
175°	767.5	768.1	768.8	769.4
177.5°	768.6	769.2	769.9	770.5
180°	769.4	769.4	769.4	769.4

(END OF REPORT)