

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010970

Luminaire Tested: S123RDIP-B775D1025UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010970
REPORT IS A COMBINATION OF REPORTS P993526 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B775D1025UB2750-4F0-XX-W2A-A_3000K
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7118.0 lumens
Efficiency: N/A
Efficacy: 110.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010970

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010970

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43
2	88	81	76	71	81	75	70	66	62	59	56	51	48	46	40	38	37
3	81	72	65	60	74	66	60	55	55	51	47	45	42	40	36	34	32
4	74	64	56	51	68	59	52	47	49	45	41	41	37	34	32	30	28
5	68	57	49	44	62	53	46	41	44	39	35	37	33	30	29	27	25
6	63	51	44	38	58	48	41	36	40	35	31	33	29	26	27	24	22
7	58	47	39	34	53	43	36	31	37	31	27	30	26	24	25	22	20
8	54	42	35	30	50	39	33	28	33	28	24	28	24	21	23	20	18
9	50	39	31	27	46	36	29	25	31	26	22	26	22	19	21	18	16
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13232	13232	13232	13232
5°	13242	15240	13276	11306
10°	13125	18396	13182	9875
15°	12990	20879	12990	8707
20°	12724	22521	12795	7724
25°	12529	21397	12504	7048
30°	12302	14825	12277	6387
35°	12028	9518	11974	5888
40°	11689	6721	11631	5393
45°	11098	5379	11082	4909
50°	10371	4500	10337	4344
55°	9554	3708	9478	3683
60°	8751	3065	8664	3132
65°	7810	2453	7861	2656
70°	6944	1705	7130	2146
75°	5885	1265	6124	1650
80°	4685	838	5087	1238
85°	3333	397	3640	769

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 17665 cd/sqm

TEST NUMBER: P1010970

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.7	1.7
10°-20°	377.9	5.3
20°-30°	595.2	8.4
30°-40°	618.9	8.7
40°-50°	529.5	7.4
50°-60°	403.7	5.7
60°-70°	258.6	3.6
70°-80°	123.9	1.7
80°-90°	35.2	0.5
90°-100°	46.9	0.7
100°-110°	226.7	3.2
110°-120°	555.6	7.8
120°-130°	705.4	9.9
130°-140°	753.5	10.6
140°-150°	704.6	9.9
150°-160°	568.4	8.0
160°-170°	366.8	5.2
170°-180°	126.4	1.8
0°-30°	1093.8	15.4
0°-40°	1712.7	24.1
0°-60°	2645.9	37.2
0°-90°	3063.7	43.0
90°-120°	829.3	11.7
90°-150°	2992.8	42.0
90°-180°	4054.0	57.0
0°-180°	7118.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1229	1229	1229	1229	1229	
5°	1228	1460	1231	1083	1228	116
15°	1174	2074	1174	865	1174	330
25°	1067	2138	1065	704	1067	492
35°	931	927	927	574	931	583
45°	747	495	746	452	747	575
55°	527	310	523	308	527	472
65°	323	179	325	194	323	323
75°	155	76	161	99	155	167
85°	35	18	38	35	35	39
90°	1	30	1	30	1	5
95°	60	38	60	38	60	72
105°	294	44	294	44	294	312
115°	552	581	552	581	552	545
125°	779	794	779	794	779	696
135°	969	979	969	979	969	746
145°	1118	1129	1118	1129	1118	700
155°	1232	1230	1232	1230	1232	568
165°	1299	1296	1299	1296	1299	367
175°	1330	1325	1330	1325	1330	127
180°	1330	1330	1330	1330	1330	

TEST NUMBER: P1010970

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3
2.5°	1232.4	1240.9	1247.2	1251.4	1261.9	1268.2	1273.5	1283.0	1283.0	1285.1	1289.3
5°	1228.2	1246.1	1258.8	1275.6	1297.7	1308.2	1323.0	1335.6	1353.5	1363.0	1372.4
7.5°	1218.8	1244.0	1270.3	1295.6	1328.2	1349.3	1364.0	1396.6	1419.8	1448.2	1470.3
10°	1206.1	1240.9	1274.5	1313.5	1357.7	1389.3	1411.4	1454.5	1498.7	1538.7	1572.4
12.5°	1190.3	1232.4	1280.9	1328.2	1390.3	1421.9	1457.7	1511.4	1574.5	1625.0	1670.3
15°	1173.5	1221.9	1276.7	1334.5	1412.4	1456.6	1508.2	1573.4	1644.0	1716.6	1778.7
17.5°	1147.2	1208.2	1269.3	1353.5	1445.0	1471.4	1515.6	1605.0	1692.4	1757.6	1833.4
20°	1120.9	1189.3	1266.1	1341.9	1440.8	1501.9	1542.9	1637.7	1731.3	1810.3	1882.9
22.5°	1096.7	1168.2	1248.2	1344.0	1436.6	1497.7	1549.2	1648.2	1756.6	1845.0	1934.4
25°	1067.2	1145.1	1233.5	1324.0	1436.6	1482.9	1539.8	1654.5	1769.2	1871.3	1981.8
27.5°	1035.6	1114.6	1201.9	1294.5	1397.7	1466.1	1521.9	1645.0	1785.0	1894.5	2008.1
30°	1004.1	1085.1	1169.3	1252.4	1368.2	1433.5	1497.7	1633.4	1793.4	1918.7	2006.0
32.5°	973.5	1041.9	1125.1	1206.1	1320.9	1392.4	1465.0	1621.9	1796.6	1901.8	1943.9
35°	931.4	1003.0	1070.4	1156.7	1272.4	1343.0	1428.2	1620.8	1782.9	1848.1	1827.1
37.5°	892.5	952.5	1016.7	1093.5	1212.5	1304.0	1392.4	1593.4	1737.6	1741.8	1622.9
40°	849.3	898.8	952.5	1033.5	1161.9	1252.4	1348.2	1551.3	1655.5	1593.4	1384.0
42.5°	799.9	844.1	886.2	965.1	1105.1	1206.1	1309.3	1498.7	1536.6	1393.5	1175.6
45°	747.3	783.0	822.0	905.1	1045.1	1145.1	1248.2	1417.7	1378.7	1176.7	969.3
47.5°	692.5	723.0	760.9	836.7	980.9	1083.0	1180.9	1301.9	1203.0	986.2	812.5
50°	637.8	662.0	698.8	776.7	915.7	1008.3	1098.8	1177.7	1038.8	846.2	671.5
52.5°	584.1	603.1	641.0	707.3	842.0	930.4	995.6	1026.2	885.1	698.8	583.1
55°	527.3	548.3	573.6	641.0	774.6	839.9	883.0	882.0	736.7	592.5	482.0
57.5°	472.6	491.5	513.6	581.0	689.4	733.6	770.4	752.5	614.6	485.2	413.6
60°	424.1	434.7	458.9	515.7	597.8	635.7	656.7	626.2	502.0	409.4	342.1
62.5°	371.5	382.0	402.0	455.7	506.2	526.2	544.1	505.2	414.7	333.6	292.6
65°	323.1	336.8	349.4	392.6	419.9	444.1	442.0	409.4	324.2	271.5	237.9
67.5°	281.0	286.3	296.8	323.1	335.7	353.6	354.7	317.8	261.0	221.0	201.0
70°	235.8	241.0	248.4	261.0	269.4	273.6	271.5	238.9	196.8	172.6	154.7
72.5°	196.8	195.8	201.0	201.0	209.4	208.4	202.1	176.8	149.5	129.5	118.9
75°	154.7	155.8	156.8	154.7	151.6	147.3	142.1	123.1	105.2	95.8	86.3
77.5°	121.0	118.9	120.0	112.6	108.4	104.2	96.8	87.4	72.6	70.5	66.3
80°	86.3	85.3	84.2	81.0	71.6	67.4	62.1	56.8	53.7	51.6	50.5
82.5°	57.9	57.9	55.8	49.5	44.2	41.0	40.0	37.9	34.7	34.7	33.7
85°	34.7	33.7	31.6	25.3	22.1	22.1	22.1	22.1	20.0	20.0	18.9
87.5°	13.7	12.6	9.5	9.5	8.4	8.4	8.4	7.4	7.4	6.3	6.3
90°	1.0	3.2	5.4	7.6	9.8	10.9	12.3	15.2	18.0	20.9	23.7
92.5°	22.7	21.4	20.1	18.8	17.5	16.8	17.8	19.8	21.7	23.7	25.7
95°	60.3	51.3	42.3	33.3	24.3	19.8	21.0	23.4	25.8	28.2	30.6
97.5°	109.7	103.5	97.4	91.2	85.1	82.0	76.4	65.2	54.0	42.8	31.6
100°	167.0	171.4	175.8	180.1	184.5	186.7	169.6	135.3	101.1	66.8	32.6
102.5°	232.2	235.0	237.9	240.7	243.6	245.0	225.9	187.7	149.5	111.3	73.1
105°	294.4	296.8	299.2	301.7	304.1	305.3	295.4	275.7	255.9	236.2	216.4
107.5°	360.6	362.6	364.6	366.5	368.5	369.5	371.1	374.4	377.7	381.0	384.3
110°	426.8	428.6	430.3	432.1	433.8	434.7	435.9	438.3	440.8	443.2	445.6

TEST NUMBER: P1010970

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	490.1	491.6	493.2	494.7	496.2	497.0	498.2	500.6	503.1	505.5	507.9
115°	552.3	553.6	554.9	556.2	557.5	558.2	559.2	561.2	563.1	565.1	567.1
117.5°	613.6	615.1	616.7	618.2	619.7	620.5	621.0	622.1	623.2	624.3	625.4
120°	669.9	671.9	673.9	675.8	677.8	678.8	679.1	679.8	680.5	681.1	681.8
122.5°	727.2	728.7	730.3	731.8	733.3	734.1	734.5	735.4	736.3	737.2	738.1
125°	778.6	780.4	782.1	783.9	785.6	786.5	786.9	787.8	788.7	789.5	790.4
127.5°	830.0	831.8	833.5	835.3	837.0	837.9	838.4	839.5	840.6	841.7	842.8
130°	877.4	879.2	880.9	882.7	884.4	885.3	885.7	886.6	887.5	888.3	889.2
132.5°	922.8	924.6	926.3	928.1	929.8	930.7	931.0	931.7	932.4	933.0	933.7
135°	969.3	970.6	971.9	973.2	974.5	975.2	975.6	976.5	977.4	978.3	979.2
137.5°	1008.8	1010.6	1012.3	1014.1	1015.8	1016.7	1016.9	1017.4	1017.8	1018.3	1018.7
140°	1048.3	1049.6	1050.9	1052.2	1053.5	1054.2	1054.5	1055.2	1055.9	1056.5	1057.2
142.5°	1084.9	1086.2	1087.5	1088.8	1090.1	1090.8	1091.1	1091.8	1092.5	1093.1	1093.8
145°	1118.5	1120.0	1121.6	1123.1	1124.6	1125.4	1125.6	1126.1	1126.5	1127.0	1127.4
147.5°	1151.1	1152.2	1153.3	1154.4	1155.5	1156.0	1156.2	1156.7	1157.1	1157.6	1158.0
150°	1180.7	1181.4	1182.0	1182.7	1183.4	1183.7	1183.9	1184.4	1184.8	1185.3	1185.7
152.5°	1207.4	1207.6	1207.8	1208.1	1208.3	1208.4	1208.5	1208.7	1209.0	1209.2	1209.4
155°	1232.1	1231.7	1231.2	1230.8	1230.3	1230.1	1230.2	1230.4	1230.7	1230.9	1231.1
157.5°	1251.9	1251.9	1251.9	1251.9	1251.9	1251.9	1251.8	1251.6	1251.3	1251.1	1250.9
160°	1269.6	1269.4	1269.2	1269.0	1268.8	1268.7	1268.6	1268.4	1268.1	1267.9	1267.7
162.5°	1286.4	1285.8	1285.1	1284.5	1283.8	1283.5	1283.4	1283.2	1282.9	1282.7	1282.5
165°	1299.3	1298.6	1298.0	1297.3	1296.6	1296.3	1296.2	1296.0	1295.7	1295.5	1295.3
167.5°	1310.1	1309.2	1308.4	1307.5	1306.6	1306.2	1306.2	1306.2	1306.2	1306.2	1306.2
170°	1319.0	1318.1	1317.3	1316.4	1315.5	1315.1	1315.1	1315.1	1315.1	1315.1	1315.1
172.5°	1325.0	1323.9	1322.8	1321.7	1320.6	1320.0	1320.1	1320.3	1320.6	1320.8	1321.0
175°	1329.9	1328.8	1327.7	1326.6	1325.5	1325.0	1325.1	1325.3	1325.6	1325.8	1326.0
177.5°	1331.9	1330.8	1329.7	1328.6	1327.5	1326.9	1327.0	1327.2	1327.5	1327.7	1327.9
180°	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9

TEST NUMBER: P1010970

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3
2.5°	1297.7	1297.7	1307.2	1316.6	1311.4	1314.5	1326.1	1321.9	1330.3	1329.3	1332.4
5°	1395.6	1407.2	1416.6	1436.6	1439.8	1436.6	1456.6	1461.9	1471.4	1459.8	1465.0
7.5°	1506.1	1530.3	1553.5	1582.9	1592.4	1594.5	1605.0	1619.8	1632.4	1609.2	1620.8
10°	1613.4	1650.3	1697.6	1724.0	1747.1	1755.5	1763.9	1773.4	1788.2	1801.8	1791.3
12.5°	1729.2	1782.9	1828.1	1875.5	1903.9	1900.8	1925.0	1931.3	1942.9	1946.0	1950.2
15°	1823.9	1899.7	1928.1	1998.6	2005.0	2026.0	2053.4	2077.6	2080.7	2074.4	2074.4
17.5°	1914.5	1979.7	2030.2	2087.1	2098.6	2116.5	2151.3	2162.8	2167.0	2166.0	2166.0
20°	1988.1	2031.3	2116.5	2163.9	2182.8	2206.0	2230.2	2244.9	2248.1	2252.3	2246.0
22.5°	2036.5	2101.8	2171.3	2210.2	2226.0	2234.4	2250.2	2254.4	2249.1	2250.2	2251.2
25°	2074.4	2138.6	2180.7	2191.3	2190.2	2179.7	2168.1	2148.1	2146.0	2137.6	2120.7
27.5°	2085.0	2109.2	2103.9	2060.7	2017.6	2013.4	1943.9	1906.0	1862.9	1869.2	1845.0
30°	2028.1	1996.5	1921.8	1812.4	1767.1	1693.4	1615.5	1534.5	1502.9	1468.2	1532.4
32.5°	1889.2	1776.6	1644.0	1501.9	1426.1	1360.8	1277.7	1218.8	1185.1	1156.7	1211.4
35°	1679.7	1504.0	1328.2	1193.5	1131.4	1072.5	994.6	965.1	923.0	927.2	932.5
37.5°	1410.3	1216.7	1084.0	951.4	910.4	886.2	829.3	784.1	769.4	765.1	765.1
40°	1157.7	998.8	880.9	776.7	745.2	725.2	679.9	658.8	643.1	638.9	644.1
42.5°	957.8	822.0	730.4	661.0	638.9	613.6	594.6	568.3	565.2	557.8	567.3
45°	804.1	686.2	617.8	567.3	548.3	538.9	517.8	502.0	495.7	494.7	502.0
47.5°	682.0	590.4	530.4	498.9	484.1	474.7	456.8	450.5	444.1	446.2	443.1
50°	572.5	504.1	465.2	436.8	427.3	417.8	406.3	399.9	396.8	396.8	395.7
52.5°	491.5	434.7	409.4	383.1	378.9	373.6	361.0	356.8	351.5	350.5	354.7
55°	421.0	382.0	356.8	341.0	336.8	326.3	321.0	315.7	312.6	310.5	311.5
57.5°	359.9	330.5	313.6	300.0	292.6	288.4	278.9	277.9	275.7	275.7	274.7
60°	309.4	288.4	268.4	260.0	254.7	249.4	248.4	242.1	238.9	241.0	240.0
62.5°	262.1	245.2	233.6	224.2	221.0	216.8	213.7	211.5	208.4	209.4	209.4
65°	218.9	205.2	196.8	188.4	187.3	183.1	182.1	180.0	180.0	178.9	181.0
67.5°	180.0	170.5	163.1	157.9	154.7	155.8	151.6	148.4	148.4	147.3	150.5
70°	143.1	137.9	130.5	124.2	120.0	120.0	114.7	113.7	113.7	113.7	112.6
72.5°	110.5	101.0	97.9	95.8	95.8	95.8	93.7	93.7	92.6	93.7	92.6
75°	82.1	81.0	78.9	77.9	77.9	76.8	75.8	75.8	75.8	75.8	75.8
77.5°	64.2	64.2	62.1	61.0	61.0	61.0	60.0	60.0	58.9	58.9	58.9
80°	47.4	47.4	45.3	45.3	45.3	44.2	44.2	44.2	45.3	44.2	44.2
82.5°	32.6	32.6	31.6	32.6	31.6	30.5	30.5	30.5	29.5	30.5	30.5
85°	18.9	18.9	17.9	16.8	17.9	17.9	16.8	17.9	16.8	17.9	16.8
87.5°	7.4	6.3	6.3	6.3	5.3	6.3	5.3	5.3	6.3	5.3	6.3
90°	24.6	25.5	26.4	27.3	27.7	27.9	28.3	28.8	29.2	29.6	29.2
92.5°	27.2	28.8	30.3	31.8	32.6	32.7	32.9	33.2	33.4	33.6	33.4
95°	32.1	33.7	35.2	36.7	37.5	37.5	37.5	37.5	37.5	37.5	37.5
97.5°	33.4	35.1	36.9	38.6	39.5	39.6	39.8	40.1	40.3	40.5	40.3
100°	34.4	36.1	37.9	39.6	40.5	40.6	40.8	41.1	41.3	41.5	41.3
102.5°	65.9	58.6	51.4	44.1	40.5	40.7	41.2	41.6	42.1	42.5	42.1
105°	177.5	138.7	99.8	60.9	41.5	41.7	42.2	42.6	43.1	43.5	43.1
107.5°	350.5	316.7	282.9	249.1	232.2	217.8	189.1	160.3	131.6	102.8	131.6
110°	438.4	431.1	423.9	416.6	413.0	397.3	365.9	334.5	303.1	271.7	303.1

TEST NUMBER: P1010970

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	509.9	511.8	513.8	515.7	516.7	516.5	516.1	515.6	515.2	514.8	515.2
115°	569.3	571.5	573.7	575.9	577.0	577.4	578.3	579.2	580.1	581.0	580.1
117.5°	627.2	628.9	630.7	632.4	633.3	633.4	633.6	633.9	634.1	634.3	634.1
120°	683.6	685.3	687.1	688.8	689.7	689.7	689.7	689.7	689.7	689.7	689.7
122.5°	739.2	740.3	741.4	742.5	743.0	743.1	743.3	743.6	743.8	744.0	743.8
125°	790.8	791.3	791.7	792.2	792.4	792.6	793.1	793.5	794.0	794.4	794.0
127.5°	843.5	844.1	844.8	845.5	845.8	845.6	845.1	844.7	844.2	843.8	844.2
130°	890.1	891.0	891.9	892.8	893.2	893.0	892.5	892.1	891.6	891.2	891.6
132.5°	934.6	935.5	936.4	937.3	937.7	937.4	936.7	936.0	935.4	934.7	935.4
135°	979.8	980.5	981.1	981.8	982.1	981.8	981.1	980.5	979.8	979.2	979.8
137.5°	1019.8	1020.9	1022.0	1023.1	1023.6	1023.4	1022.9	1022.5	1022.0	1021.6	1022.0
140°	1058.1	1059.0	1059.9	1060.8	1061.2	1061.0	1060.5	1060.1	1059.6	1059.2	1059.6
142.5°	1094.4	1095.1	1095.7	1096.4	1096.7	1096.4	1095.7	1095.1	1094.4	1093.8	1094.4
145°	1127.8	1128.2	1128.7	1129.1	1129.3	1129.3	1129.3	1129.3	1129.3	1129.3	1129.3
147.5°	1158.4	1158.9	1159.3	1159.8	1160.0	1159.4	1158.3	1157.2	1156.1	1155.0	1156.1
150°	1186.1	1186.5	1187.0	1187.4	1187.6	1187.3	1186.6	1186.0	1185.3	1184.7	1185.3
152.5°	1210.3	1211.1	1212.0	1212.9	1213.3	1212.8	1211.7	1210.6	1209.5	1208.4	1209.5
155°	1232.2	1233.3	1234.4	1235.5	1236.0	1235.3	1234.0	1232.7	1231.4	1230.1	1231.4
157.5°	1252.2	1253.5	1254.8	1256.1	1256.8	1255.9	1254.2	1252.4	1250.7	1248.9	1250.7
160°	1269.0	1270.3	1271.6	1272.9	1273.6	1272.8	1271.3	1269.8	1268.2	1266.7	1268.2
162.5°	1284.0	1285.6	1287.1	1288.6	1289.4	1288.7	1287.4	1286.1	1284.8	1283.5	1284.8
165°	1297.1	1298.8	1300.6	1302.3	1303.2	1302.4	1300.9	1299.4	1297.8	1296.3	1297.8
167.5°	1308.0	1309.7	1311.5	1313.2	1314.1	1313.2	1311.5	1309.7	1308.0	1306.2	1308.0
170°	1316.9	1318.6	1320.4	1322.1	1323.0	1322.1	1320.4	1318.6	1316.9	1315.1	1316.9
172.5°	1322.8	1324.5	1326.3	1328.0	1328.9	1327.9	1325.9	1324.0	1322.0	1320.0	1322.0
175°	1327.5	1329.1	1330.6	1332.1	1332.9	1332.0	1330.3	1328.5	1326.8	1325.0	1326.8
177.5°	1329.7	1331.4	1333.2	1334.9	1335.8	1334.7	1332.5	1330.4	1328.2	1326.0	1328.2
180°	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9

TEST NUMBER: P1010970

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3
2.5°	1327.2	1320.9	1316.6	1313.5	1310.3	1319.8	1307.2	1293.5	1284.0	1277.7	1275.6
5°	1466.1	1452.4	1440.8	1431.4	1433.5	1433.5	1411.4	1387.2	1366.1	1354.5	1341.9
7.5°	1627.1	1612.4	1589.2	1584.0	1579.8	1553.5	1531.4	1487.1	1460.8	1434.5	1411.4
10°	1787.1	1768.2	1746.1	1738.7	1728.2	1695.5	1661.9	1605.0	1572.4	1524.0	1493.5
12.5°	1936.6	1913.4	1891.3	1886.0	1870.2	1841.8	1783.9	1725.0	1669.2	1617.7	1564.0
15°	2061.8	2055.5	2021.8	2000.8	1966.0	1927.1	1914.5	1834.5	1763.9	1710.3	1613.4
17.5°	2167.0	2137.6	2106.0	2092.3	2078.6	2033.4	1988.1	1906.0	1830.3	1751.3	1689.2
20°	2251.2	2218.6	2196.5	2176.5	2170.2	2118.6	2047.1	1974.4	1891.3	1802.9	1721.8
22.5°	2255.5	2251.2	2236.5	2224.9	2212.3	2178.6	2121.8	2031.3	1942.9	1846.0	1739.7
25°	2168.1	2161.8	2203.9	2193.4	2201.8	2189.1	2158.6	2082.8	1979.7	1866.0	1758.7
27.5°	1905.0	1969.2	2035.5	2058.6	2074.4	2119.7	2134.4	2092.3	2009.2	1888.1	1768.2
30°	1547.1	1632.4	1739.7	1797.6	1841.8	1926.0	2035.5	2049.2	2010.2	1913.4	1766.1
32.5°	1214.6	1292.4	1378.7	1447.2	1506.1	1678.7	1826.0	1932.3	1951.3	1900.8	1771.3
35°	978.8	1012.5	1094.6	1159.8	1239.8	1387.2	1560.8	1732.4	1848.1	1854.5	1755.5
37.5°	807.2	825.1	896.7	933.5	980.9	1110.4	1272.4	1496.6	1676.6	1761.8	1711.3
40°	668.3	709.4	750.4	771.5	805.1	894.6	1050.4	1226.1	1449.3	1607.1	1642.9
42.5°	579.9	597.8	624.1	653.6	674.6	752.5	856.7	1017.7	1218.8	1438.7	1537.7
45°	511.5	517.8	545.2	564.1	586.2	641.0	714.6	849.3	1026.2	1243.0	1411.4
47.5°	454.7	467.3	482.0	493.6	508.3	550.4	613.6	711.5	867.2	1060.9	1241.9
50°	404.2	411.5	430.5	435.7	446.2	475.7	524.1	598.9	727.3	882.0	1069.3
52.5°	356.8	370.5	377.8	385.2	394.7	418.9	450.5	511.5	608.3	753.6	912.5
55°	320.0	324.2	334.7	341.0	348.4	365.2	392.6	437.8	513.6	629.4	779.9
57.5°	284.2	284.2	294.7	300.0	307.3	320.0	344.2	378.9	433.6	519.9	657.8
60°	246.3	247.3	255.8	262.1	264.2	276.8	296.8	324.2	366.3	429.4	542.0
62.5°	212.6	217.9	222.1	224.2	231.5	238.9	255.8	274.7	304.2	359.9	439.9
65°	184.2	185.2	188.4	190.5	193.7	202.1	214.7	227.3	252.6	293.6	358.9
67.5°	151.6	155.8	160.0	160.0	163.1	167.3	180.0	190.5	209.4	233.6	277.9
70°	113.7	115.8	122.1	125.2	129.5	136.8	143.1	149.5	164.2	182.1	215.8
72.5°	94.7	94.7	96.8	97.9	97.9	103.1	112.6	118.9	126.3	138.9	162.1
75°	75.8	75.8	78.9	77.9	80.0	82.1	83.1	87.4	91.6	101.0	114.7
77.5°	60.0	61.0	61.0	62.1	62.1	63.1	64.2	66.3	68.4	73.7	80.0
80°	44.2	45.3	45.3	46.3	46.3	47.4	48.4	49.5	51.6	53.7	56.8
82.5°	30.5	31.6	31.6	32.6	31.6	32.6	33.7	33.7	34.7	36.8	37.9
85°	17.9	17.9	18.9	17.9	17.9	17.9	18.9	18.9	20.0	23.2	23.2
87.5°	5.3	6.3	5.3	6.3	6.3	6.3	6.3	7.4	7.4	8.4	9.5
90°	28.8	28.3	27.9	27.7	27.3	26.4	25.5	24.6	23.7	20.9	18.0
92.5°	33.2	32.9	32.7	32.6	31.8	30.3	28.8	27.2	25.7	23.7	21.7
95°	37.5	37.5	37.5	37.5	36.7	35.2	33.7	32.1	30.6	28.2	25.8
97.5°	40.1	39.8	39.6	39.5	38.6	36.9	35.1	33.4	31.6	42.8	54.0
100°	41.1	40.8	40.6	40.5	39.6	37.9	36.1	34.4	32.6	66.8	101.1
102.5°	41.6	41.2	40.7	40.5	44.1	51.4	58.6	65.9	73.1	111.3	149.5
105°	42.6	42.2	41.7	41.5	60.9	99.8	138.7	177.5	216.4	236.2	255.9
107.5°	160.3	189.1	217.8	232.2	249.1	282.9	316.7	350.5	384.3	381.0	377.7
110°	334.5	365.9	397.3	413.0	416.6	423.9	431.1	438.4	445.6	443.2	440.8

TEST NUMBER: P1010970

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	515.6	516.1	516.5	516.7	515.7	513.8	511.8	509.9	507.9	505.5	503.1
115°	579.2	578.3	577.4	577.0	575.9	573.7	571.5	569.3	567.1	565.1	563.1
117.5°	633.9	633.6	633.4	633.3	632.4	630.7	628.9	627.2	625.4	624.3	623.2
120°	689.7	689.7	689.7	689.7	688.8	687.1	685.3	683.6	681.8	681.1	680.5
122.5°	743.6	743.3	743.1	743.0	742.5	741.4	740.3	739.2	738.1	737.2	736.3
125°	793.5	793.1	792.6	792.4	792.2	791.7	791.3	790.8	790.4	789.5	788.7
127.5°	844.7	845.1	845.6	845.8	845.5	844.8	844.1	843.5	842.8	841.7	840.6
130°	892.1	892.5	893.0	893.2	892.8	891.9	891.0	890.1	889.2	888.3	887.5
132.5°	936.0	936.7	937.4	937.7	937.3	936.4	935.5	934.6	933.7	933.0	932.4
135°	980.5	981.1	981.8	982.1	981.8	981.1	980.5	979.8	979.2	978.3	977.4
137.5°	1022.5	1022.9	1023.4	1023.6	1023.1	1022.0	1020.9	1019.8	1018.7	1018.3	1017.8
140°	1060.1	1060.5	1061.0	1061.2	1060.8	1059.9	1059.0	1058.1	1057.2	1056.5	1055.9
142.5°	1095.1	1095.7	1096.4	1096.7	1096.4	1095.7	1095.1	1094.4	1093.8	1093.1	1092.5
145°	1129.3	1129.3	1129.3	1129.3	1129.1	1128.7	1128.2	1127.8	1127.4	1127.0	1126.5
147.5°	1157.2	1158.3	1159.4	1160.0	1159.8	1159.3	1158.9	1158.4	1158.0	1157.6	1157.1
150°	1186.0	1186.6	1187.3	1187.6	1187.4	1187.0	1186.5	1186.1	1185.7	1185.3	1184.8
152.5°	1210.6	1211.7	1212.8	1213.3	1212.9	1212.0	1211.1	1210.3	1209.4	1209.2	1209.0
155°	1232.7	1234.0	1235.3	1236.0	1235.5	1234.4	1233.3	1232.2	1231.1	1230.9	1230.7
157.5°	1252.4	1254.2	1255.9	1256.8	1256.1	1254.8	1253.5	1252.2	1250.9	1251.1	1251.3
160°	1269.8	1271.3	1272.8	1273.6	1272.9	1271.6	1270.3	1269.0	1267.7	1267.9	1268.1
162.5°	1286.1	1287.4	1288.7	1289.4	1288.6	1287.1	1285.6	1284.0	1282.5	1282.7	1282.9
165°	1299.4	1300.9	1302.4	1303.2	1302.3	1300.6	1298.8	1297.1	1295.3	1295.5	1295.7
167.5°	1309.7	1311.5	1313.2	1314.1	1313.2	1311.5	1309.7	1308.0	1306.2	1306.2	1306.2
170°	1318.6	1320.4	1322.1	1323.0	1322.1	1320.4	1318.6	1316.9	1315.1	1315.1	1315.1
172.5°	1324.0	1325.9	1327.9	1328.9	1328.0	1326.3	1324.5	1322.8	1321.0	1320.8	1320.6
175°	1328.5	1330.3	1332.0	1332.9	1332.1	1330.6	1329.1	1327.5	1326.0	1325.8	1325.6
177.5°	1330.4	1332.5	1334.7	1335.8	1334.9	1333.2	1331.4	1329.7	1327.9	1327.7	1327.5
180°	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9

TEST NUMBER: P1010970

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3
2.5°	1272.4	1267.2	1261.9	1261.9	1250.3	1239.8	1234.6	1236.7	1230.3	1221.9	1213.5
5°	1328.2	1307.2	1303.0	1291.4	1275.6	1253.5	1241.9	1231.4	1218.8	1201.9	1186.1
7.5°	1379.8	1352.4	1337.7	1326.1	1295.6	1265.1	1239.8	1223.0	1200.9	1175.6	1156.7
10°	1447.2	1396.6	1380.8	1354.5	1311.4	1268.2	1238.8	1211.4	1180.9	1151.4	1126.1
12.5°	1500.8	1442.9	1413.5	1387.2	1331.4	1276.7	1227.2	1193.5	1156.7	1124.0	1091.4
15°	1561.9	1496.6	1445.0	1413.5	1343.0	1276.7	1220.9	1173.5	1132.5	1092.5	1064.1
17.5°	1591.3	1509.2	1486.1	1440.8	1338.7	1272.4	1204.0	1153.5	1104.0	1057.7	1024.1
20°	1637.7	1541.9	1484.0	1453.5	1363.0	1265.1	1185.1	1127.2	1075.6	1026.2	990.4
22.5°	1640.8	1536.6	1498.7	1440.8	1329.3	1243.0	1168.2	1097.7	1037.7	991.4	954.6
25°	1633.4	1527.1	1474.5	1428.2	1335.6	1230.3	1134.6	1065.1	1006.2	952.5	909.3
27.5°	1630.3	1499.8	1450.3	1404.0	1299.8	1193.5	1114.6	1035.6	968.3	920.9	876.7
30°	1626.1	1470.3	1410.3	1356.6	1260.9	1165.1	1070.4	1002.0	937.8	877.8	833.6
32.5°	1598.7	1430.3	1369.3	1312.4	1209.3	1113.5	1038.8	966.2	896.7	840.9	800.9
35°	1590.3	1393.5	1313.5	1252.4	1151.4	1066.2	987.2	927.2	862.0	806.2	758.8
37.5°	1566.1	1355.6	1269.3	1191.4	1086.2	1005.1	947.2	887.2	824.1	764.1	726.2
40°	1524.0	1311.4	1213.5	1133.5	1025.1	943.0	889.3	845.1	783.0	729.4	683.1
42.5°	1461.9	1266.1	1160.9	1076.7	956.7	879.9	835.7	793.6	740.9	685.2	647.3
45°	1390.3	1206.1	1108.3	1014.6	892.5	817.8	771.5	746.2	697.8	650.4	606.2
47.5°	1292.4	1144.0	1047.2	950.4	826.2	753.6	716.7	691.5	657.8	606.2	570.4
50°	1169.3	1064.1	972.5	886.2	760.9	691.5	654.6	635.7	607.3	570.4	535.7
52.5°	1032.5	971.4	895.7	815.7	694.6	629.4	595.7	581.0	559.9	525.2	495.7
55°	894.6	868.3	816.7	737.8	625.2	571.5	542.0	523.1	507.3	482.0	456.8
57.5°	771.5	758.8	723.0	662.0	567.3	511.5	486.2	473.6	461.0	442.0	416.8
60°	644.1	657.8	621.0	590.4	504.1	455.7	433.6	419.9	413.6	396.8	381.0
62.5°	533.6	546.2	525.2	502.0	441.0	397.8	384.2	371.5	367.3	352.6	336.8
65°	433.6	449.4	433.6	421.0	384.2	348.4	331.5	325.2	321.0	311.5	298.9
67.5°	345.2	361.0	353.6	337.8	326.3	296.8	287.3	281.0	278.9	271.5	261.0
70°	260.0	282.1	284.2	274.7	264.2	250.5	244.2	242.1	236.8	230.5	224.2
72.5°	187.3	212.6	213.7	213.7	207.3	207.3	201.0	197.9	197.9	191.6	184.2
75°	137.9	154.7	156.8	158.9	162.1	165.2	161.0	161.0	160.0	153.7	150.5
77.5°	91.6	106.3	111.6	118.9	123.1	123.1	125.2	127.3	125.2	122.1	120.0
80°	58.9	69.5	75.8	80.0	86.3	89.5	92.6	93.7	91.6	90.5	87.4
82.5°	38.9	42.1	45.3	50.5	57.9	63.1	63.1	62.1	64.2	63.1	62.1
85°	22.1	24.2	25.3	26.3	30.5	35.8	36.8	37.9	40.0	37.9	35.8
87.5°	8.4	9.5	9.5	9.5	11.6	12.6	15.8	20.0	18.9	16.8	16.8
90°	15.2	12.3	10.9	9.8	7.6	5.4	3.2	1.0	3.2	5.4	7.6
92.5°	19.8	17.8	16.8	17.5	18.8	20.1	21.4	22.7	21.4	20.1	18.8
95°	23.4	21.0	19.8	24.3	33.3	42.3	51.3	60.3	51.3	42.3	33.3
97.5°	65.2	76.4	82.0	85.1	91.2	97.4	103.5	109.7	103.5	97.4	91.2
100°	135.3	169.6	186.7	184.5	180.1	175.8	171.4	167.0	171.4	175.8	180.1
102.5°	187.7	225.9	245.0	243.6	240.7	237.9	235.0	232.2	235.0	237.9	240.7
105°	275.7	295.4	305.3	304.1	301.7	299.2	296.8	294.4	296.8	299.2	301.7
107.5°	374.4	371.1	369.5	368.5	366.5	364.6	362.6	360.6	362.6	364.6	366.5
110°	438.3	435.9	434.7	433.8	432.1	430.3	428.6	426.8	428.6	430.3	432.1

TEST NUMBER: P1010970

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	500.6	498.2	497.0	496.2	494.7	493.2	491.6	490.1	491.6	493.2	494.7
115°	561.2	559.2	558.2	557.5	556.2	554.9	553.6	552.3	553.6	554.9	556.2
117.5°	622.1	621.0	620.5	619.7	618.2	616.7	615.1	613.6	615.1	616.7	618.2
120°	679.8	679.1	678.8	677.8	675.8	673.9	671.9	669.9	671.9	673.9	675.8
122.5°	735.4	734.5	734.1	733.3	731.8	730.3	728.7	727.2	728.7	730.3	731.8
125°	787.8	786.9	786.5	785.6	783.9	782.1	780.4	778.6	780.4	782.1	783.9
127.5°	839.5	838.4	837.9	837.0	835.3	833.5	831.8	830.0	831.8	833.5	835.3
130°	886.6	885.7	885.3	884.4	882.7	880.9	879.2	877.4	879.2	880.9	882.7
132.5°	931.7	931.0	930.7	929.8	928.1	926.3	924.6	922.8	924.6	926.3	928.1
135°	976.5	975.6	975.2	974.5	973.2	971.9	970.6	969.3	970.6	971.9	973.2
137.5°	1017.4	1016.9	1016.7	1015.8	1014.1	1012.3	1010.6	1008.8	1010.6	1012.3	1014.1
140°	1055.2	1054.5	1054.2	1053.5	1052.2	1050.9	1049.6	1048.3	1049.6	1050.9	1052.2
142.5°	1091.8	1091.1	1090.8	1090.1	1088.8	1087.5	1086.2	1084.9	1086.2	1087.5	1088.8
145°	1126.1	1125.6	1125.4	1124.6	1123.1	1121.6	1120.0	1118.5	1120.0	1121.6	1123.1
147.5°	1156.7	1156.2	1156.0	1155.5	1154.4	1153.3	1152.2	1151.1	1152.2	1153.3	1154.4
150°	1184.4	1183.9	1183.7	1183.4	1182.7	1182.0	1181.4	1180.7	1181.4	1182.0	1182.7
152.5°	1208.7	1208.5	1208.4	1208.3	1208.1	1207.8	1207.6	1207.4	1207.6	1207.8	1208.1
155°	1230.4	1230.2	1230.1	1230.3	1230.8	1231.2	1231.7	1232.1	1231.7	1231.2	1230.8
157.5°	1251.6	1251.8	1251.9	1251.9	1251.9	1251.9	1251.9	1251.9	1251.9	1251.9	1251.9
160°	1268.4	1268.6	1268.7	1268.8	1269.0	1269.2	1269.4	1269.6	1269.4	1269.2	1269.0
162.5°	1283.2	1283.4	1283.5	1283.8	1284.5	1285.1	1285.8	1286.4	1285.8	1285.1	1284.5
165°	1296.0	1296.2	1296.3	1296.6	1297.3	1298.0	1298.6	1299.3	1298.6	1298.0	1297.3
167.5°	1306.2	1306.2	1306.2	1306.6	1307.5	1308.4	1309.2	1310.1	1309.2	1308.4	1307.5
170°	1315.1	1315.1	1315.1	1315.5	1316.4	1317.3	1318.1	1319.0	1318.1	1317.3	1316.4
172.5°	1320.3	1320.1	1320.0	1320.6	1321.7	1322.8	1323.9	1325.0	1323.9	1322.8	1321.7
175°	1325.3	1325.1	1325.0	1325.5	1326.6	1327.7	1328.8	1329.9	1328.8	1327.7	1326.6
177.5°	1327.2	1327.0	1326.9	1327.5	1328.6	1329.7	1330.8	1331.9	1330.8	1329.7	1328.6
180°	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9

TEST NUMBER: P1010970

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3
2.5°	1213.5	1208.2	1206.1	1200.9	1188.2	1179.8	1170.4	1164.0	1165.1	1159.8	1163.0
5°	1175.6	1174.6	1167.2	1156.7	1138.8	1129.3	1112.5	1104.0	1099.8	1100.9	1094.6
7.5°	1144.0	1134.6	1129.3	1112.5	1095.6	1075.6	1061.9	1054.6	1048.3	1041.9	1037.7
10°	1108.3	1099.8	1091.4	1073.5	1050.4	1031.4	1012.5	1005.1	995.6	991.4	988.3
12.5°	1070.4	1065.1	1054.6	1033.5	1007.2	989.3	967.2	963.0	950.4	942.0	939.9
15°	1035.6	1032.5	1013.5	989.3	963.0	945.1	926.2	913.5	892.5	896.7	889.3
17.5°	998.8	985.1	973.5	940.9	928.3	900.9	878.8	872.5	857.8	848.3	838.8
20°	957.8	949.3	934.6	913.5	883.0	851.5	834.6	824.1	815.7	800.9	796.7
22.5°	918.8	908.3	895.7	868.3	842.0	815.7	792.5	783.0	772.5	762.0	755.7
25°	888.3	872.5	858.8	825.1	798.8	776.7	762.0	746.2	731.5	725.2	723.0
27.5°	840.9	831.5	817.8	786.2	762.0	737.8	724.1	713.6	697.8	690.4	684.1
30°	810.4	791.5	775.7	750.4	726.2	699.9	687.3	674.6	665.2	655.7	648.3
32.5°	769.4	754.6	742.0	716.7	692.5	668.3	654.6	635.7	630.4	623.1	614.6
35°	729.4	719.9	706.2	678.8	652.5	635.7	621.0	603.1	596.8	591.5	584.1
37.5°	691.5	677.8	668.3	642.0	618.9	598.9	587.3	572.5	568.3	562.0	556.8
40°	658.8	645.2	635.7	609.4	585.2	564.1	556.8	542.0	535.7	528.3	525.2
42.5°	622.0	610.4	597.8	578.9	553.6	532.6	517.8	509.4	501.0	497.8	491.5
45°	583.1	572.5	563.1	542.0	515.7	501.0	488.3	476.8	470.5	465.2	461.0
47.5°	549.4	539.9	527.3	504.1	483.1	469.4	456.8	445.2	438.9	432.6	427.3
50°	510.5	505.2	491.5	469.4	449.4	433.6	422.0	411.5	407.3	399.9	391.5
52.5°	475.7	466.2	454.7	436.8	418.9	399.9	384.2	377.8	370.5	366.3	358.9
55°	434.7	428.4	415.7	399.9	381.0	365.2	353.6	345.2	335.7	331.5	322.1
57.5°	399.9	388.4	382.0	362.1	344.2	328.4	320.0	311.5	301.0	294.7	290.5
60°	362.1	351.5	342.1	325.2	312.6	295.7	283.1	275.7	268.4	260.0	255.8
62.5°	325.2	316.8	305.2	291.5	275.7	262.1	252.6	242.1	237.9	229.4	226.3
65°	285.2	278.9	269.4	253.6	241.0	229.4	220.0	211.5	207.3	204.2	202.1
67.5°	249.4	241.0	234.7	221.0	207.3	197.9	192.6	187.3	182.1	178.9	175.8
70°	212.6	206.3	200.0	187.3	177.9	169.4	165.2	161.0	157.9	154.7	151.6
72.5°	174.7	171.6	165.2	156.8	149.5	143.1	140.0	134.7	131.6	126.3	124.2
75°	144.2	138.9	135.8	128.4	122.1	116.8	112.6	106.3	102.1	100.0	98.9
77.5°	113.7	111.6	107.4	101.0	97.9	92.6	86.3	84.2	82.1	82.1	81.0
80°	85.3	82.1	78.9	73.7	70.5	66.3	66.3	66.3	65.3	66.3	65.3
82.5°	57.9	55.8	53.7	50.5	49.5	49.5	50.5	50.5	50.5	50.5	50.5
85°	33.7	33.7	33.7	34.7	33.7	33.7	34.7	35.8	34.7	34.7	33.7
87.5°	15.8	15.8	16.8	16.8	17.9	17.9	17.9	17.9	17.9	17.9	18.9
90°	9.8	10.9	12.3	15.2	18.0	20.9	23.7	24.6	25.5	26.4	27.3
92.5°	17.5	16.8	17.8	19.8	21.7	23.7	25.7	27.2	28.8	30.3	31.8
95°	24.3	19.8	21.0	23.4	25.8	28.2	30.6	32.1	33.7	35.2	36.7
97.5°	85.1	82.0	76.4	65.2	54.0	42.8	31.6	33.4	35.1	36.9	38.6
100°	184.5	186.7	169.6	135.3	101.1	66.8	32.6	34.4	36.1	37.9	39.6
102.5°	243.6	245.0	225.9	187.7	149.5	111.3	73.1	65.9	58.6	51.4	44.1
105°	304.1	305.3	295.4	275.7	255.9	236.2	216.4	177.5	138.7	99.8	60.9
107.5°	368.5	369.5	371.1	374.4	377.7	381.0	384.3	350.5	316.7	282.9	249.1
110°	433.8	434.7	435.9	438.3	440.8	443.2	445.6	438.4	431.1	423.9	416.6

TEST NUMBER: P1010970

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	496.2	497.0	498.2	500.6	503.1	505.5	507.9	509.9	511.8	513.8	515.7
115°	557.5	558.2	559.2	561.2	563.1	565.1	567.1	569.3	571.5	573.7	575.9
117.5°	619.7	620.5	621.0	622.1	623.2	624.3	625.4	627.2	628.9	630.7	632.4
120°	677.8	678.8	679.1	679.8	680.5	681.1	681.8	683.6	685.3	687.1	688.8
122.5°	733.3	734.1	734.5	735.4	736.3	737.2	738.1	739.2	740.3	741.4	742.5
125°	785.6	786.5	786.9	787.8	788.7	789.5	790.4	790.8	791.3	791.7	792.2
127.5°	837.0	837.9	838.4	839.5	840.6	841.7	842.8	843.5	844.1	844.8	845.5
130°	884.4	885.3	885.7	886.6	887.5	888.3	889.2	890.1	891.0	891.9	892.8
132.5°	929.8	930.7	931.0	931.7	932.4	933.0	933.7	934.6	935.5	936.4	937.3
135°	974.5	975.2	975.6	976.5	977.4	978.3	979.2	979.8	980.5	981.1	981.8
137.5°	1015.8	1016.7	1016.9	1017.4	1017.8	1018.3	1018.7	1019.8	1020.9	1022.0	1023.1
140°	1053.5	1054.2	1054.5	1055.2	1055.9	1056.5	1057.2	1058.1	1059.0	1059.9	1060.8
142.5°	1090.1	1090.8	1091.1	1091.8	1092.5	1093.1	1093.8	1094.4	1095.1	1095.7	1096.4
145°	1124.6	1125.4	1125.6	1126.1	1126.5	1127.0	1127.4	1127.8	1128.2	1128.7	1129.1
147.5°	1155.5	1156.0	1156.2	1156.7	1157.1	1157.6	1158.0	1158.4	1158.9	1159.3	1159.8
150°	1183.4	1183.7	1183.9	1184.4	1184.8	1185.3	1185.7	1186.1	1186.5	1187.0	1187.4
152.5°	1208.3	1208.4	1208.5	1208.7	1209.0	1209.2	1209.4	1210.3	1211.1	1212.0	1212.9
155°	1230.3	1230.1	1230.2	1230.4	1230.7	1230.9	1231.1	1232.2	1233.3	1234.4	1235.5
157.5°	1251.9	1251.9	1251.8	1251.6	1251.3	1251.1	1250.9	1252.2	1253.5	1254.8	1256.1
160°	1268.8	1268.7	1268.6	1268.4	1268.1	1267.9	1267.7	1269.0	1270.3	1271.6	1272.9
162.5°	1283.8	1283.5	1283.4	1283.2	1282.9	1282.7	1282.5	1284.0	1285.6	1287.1	1288.6
165°	1296.6	1296.3	1296.2	1296.0	1295.7	1295.5	1295.3	1297.1	1298.8	1300.6	1302.3
167.5°	1306.6	1306.2	1306.2	1306.2	1306.2	1306.2	1306.2	1308.0	1309.7	1311.5	1313.2
170°	1315.5	1315.1	1315.1	1315.1	1315.1	1315.1	1315.1	1316.9	1318.6	1320.4	1322.1
172.5°	1320.6	1320.0	1320.1	1320.3	1320.6	1320.8	1321.0	1322.8	1324.5	1326.3	1328.0
175°	1325.5	1325.0	1325.1	1325.3	1325.6	1325.8	1326.0	1327.5	1329.1	1330.6	1332.1
177.5°	1327.5	1326.9	1327.0	1327.2	1327.5	1327.7	1327.9	1329.7	1331.4	1333.2	1334.9
180°	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9

TEST NUMBER: P1010970

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3
2.5°	1161.9	1163.0	1159.8	1153.5	1152.5	1154.6	1160.9	1158.8	1153.5	1163.0	1154.6
5°	1097.7	1092.5	1090.4	1092.5	1086.2	1083.0	1089.3	1086.2	1089.3	1090.4	1093.5
7.5°	1035.6	1036.7	1030.4	1031.4	1023.0	1025.1	1025.1	1025.1	1028.3	1030.4	1034.6
10°	982.0	984.1	976.7	977.7	971.4	967.2	970.4	976.7	976.7	976.7	978.8
12.5°	938.8	929.3	924.1	923.0	915.7	913.5	919.9	922.0	927.2	927.2	930.4
15°	885.1	883.0	878.8	878.8	860.9	865.1	867.2	874.6	885.1	876.7	878.8
17.5°	836.7	831.5	826.2	824.1	822.0	815.7	824.1	823.0	829.3	830.4	833.6
20°	793.6	789.4	778.8	779.9	782.0	772.5	777.8	777.8	784.1	790.4	797.8
22.5°	751.5	747.3	742.0	744.1	737.8	735.7	735.7	740.9	748.3	753.6	752.5
25°	718.8	711.5	708.3	705.2	702.0	704.1	700.9	706.2	711.5	714.6	711.5
27.5°	682.0	678.8	672.5	669.4	664.1	666.2	668.3	672.5	675.7	675.7	678.8
30°	646.2	642.0	639.9	636.7	636.7	632.5	633.6	637.8	641.0	644.1	648.3
32.5°	611.5	608.3	605.2	605.2	603.1	602.0	601.0	607.3	607.3	613.6	613.6
35°	583.1	577.8	577.8	572.5	574.7	573.6	571.5	575.7	576.8	581.0	579.9
37.5°	551.5	551.5	549.4	544.1	539.9	541.0	546.2	546.2	549.4	548.3	551.5
40°	519.9	517.8	517.8	514.7	513.6	512.6	513.6	514.7	519.9	518.9	519.9
42.5°	488.3	489.4	484.1	484.1	484.1	481.0	482.0	483.1	485.2	487.3	490.5
45°	457.8	455.7	454.7	452.6	450.5	451.5	450.5	454.7	453.6	455.7	458.9
47.5°	425.2	422.0	421.0	416.8	416.8	418.9	417.8	421.0	422.0	425.2	423.1
50°	393.6	389.4	386.3	387.3	381.0	383.1	383.1	386.3	389.4	390.5	392.6
52.5°	356.8	355.7	354.7	349.4	348.4	347.3	348.4	349.4	353.6	356.8	357.8
55°	321.0	320.0	313.6	311.5	308.4	308.4	310.5	311.5	318.9	320.0	324.2
57.5°	288.4	285.2	277.9	276.8	276.8	276.8	273.6	277.9	280.0	285.2	285.2
60°	252.6	252.6	246.3	246.3	247.3	246.3	246.3	247.3	247.3	251.5	253.6
62.5°	224.2	223.1	223.1	221.0	220.0	221.0	220.0	220.0	221.0	224.2	227.3
65°	198.9	197.9	196.8	195.8	193.7	193.7	194.7	196.8	196.8	198.9	200.0
67.5°	174.7	174.7	172.6	172.6	171.6	170.5	171.6	170.5	174.7	174.7	175.8
70°	150.5	149.5	146.3	145.2	142.1	143.1	143.1	146.3	147.3	149.5	151.6
72.5°	121.0	121.0	118.9	116.8	117.9	115.8	115.8	116.8	116.8	120.0	121.0
75°	100.0	97.9	96.8	97.9	96.8	98.9	96.8	96.8	98.9	98.9	98.9
77.5°	82.1	82.1	81.0	81.0	82.1	81.0	82.1	82.1	82.1	81.0	82.1
80°	67.4	66.3	66.3	66.3	65.3	65.3	65.3	65.3	65.3	65.3	65.3
82.5°	50.5	50.5	49.5	50.5	50.5	49.5	50.5	49.5	49.5	50.5	50.5
85°	33.7	35.8	33.7	33.7	34.7	34.7	35.8	34.7	35.8	33.7	34.7
87.5°	17.9	18.9	18.9	17.9	17.9	18.9	18.9	18.9	20.0	17.9	18.9
90°	27.7	27.9	28.3	28.8	29.2	29.6	29.2	28.8	28.3	27.9	27.7
92.5°	32.6	32.7	32.9	33.2	33.4	33.6	33.4	33.2	32.9	32.7	32.6
95°	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5
97.5°	39.5	39.6	39.8	40.1	40.3	40.5	40.3	40.1	39.8	39.6	39.5
100°	40.5	40.6	40.8	41.1	41.3	41.5	41.3	41.1	40.8	40.6	40.5
102.5°	40.5	40.7	41.2	41.6	42.1	42.5	42.1	41.6	41.2	40.7	40.5
105°	41.5	41.7	42.2	42.6	43.1	43.5	43.1	42.6	42.2	41.7	41.5
107.5°	232.2	217.8	189.1	160.3	131.6	102.8	131.6	160.3	189.1	217.8	232.2
110°	413.0	397.3	365.9	334.5	303.1	271.7	303.1	334.5	365.9	397.3	413.0

TEST NUMBER: P1010970

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	516.7	516.5	516.1	515.6	515.2	514.8	515.2	515.6	516.1	516.5	516.7
115°	577.0	577.4	578.3	579.2	580.1	581.0	580.1	579.2	578.3	577.4	577.0
117.5°	633.3	633.4	633.6	633.9	634.1	634.3	634.1	633.9	633.6	633.4	633.3
120°	689.7	689.7	689.7	689.7	689.7	689.7	689.7	689.7	689.7	689.7	689.7
122.5°	743.0	743.1	743.3	743.6	743.8	744.0	743.8	743.6	743.3	743.1	743.0
125°	792.4	792.6	793.1	793.5	794.0	794.4	794.0	793.5	793.1	792.6	792.4
127.5°	845.8	845.6	845.1	844.7	844.2	843.8	844.2	844.7	845.1	845.6	845.8
130°	893.2	893.0	892.5	892.1	891.6	891.2	891.6	892.1	892.5	893.0	893.2
132.5°	937.7	937.4	936.7	936.0	935.4	934.7	935.4	936.0	936.7	937.4	937.7
135°	982.1	981.8	981.1	980.5	979.8	979.2	979.8	980.5	981.1	981.8	982.1
137.5°	1023.6	1023.4	1022.9	1022.5	1022.0	1021.6	1022.0	1022.5	1022.9	1023.4	1023.6
140°	1061.2	1061.0	1060.5	1060.1	1059.6	1059.2	1059.6	1060.1	1060.5	1061.0	1061.2
142.5°	1096.7	1096.4	1095.7	1095.1	1094.4	1093.8	1094.4	1095.1	1095.7	1096.4	1096.7
145°	1129.3	1129.3	1129.3	1129.3	1129.3	1129.3	1129.3	1129.3	1129.3	1129.3	1129.3
147.5°	1160.0	1159.4	1158.3	1157.2	1156.1	1155.0	1156.1	1157.2	1158.3	1159.4	1160.0
150°	1187.6	1187.3	1186.6	1186.0	1185.3	1184.7	1185.3	1186.0	1186.6	1187.3	1187.6
152.5°	1213.3	1212.8	1211.7	1210.6	1209.5	1208.4	1209.5	1210.6	1211.7	1212.8	1213.3
155°	1236.0	1235.3	1234.0	1232.7	1231.4	1230.1	1231.4	1232.7	1234.0	1235.3	1236.0
157.5°	1256.8	1255.9	1254.2	1252.4	1250.7	1248.9	1250.7	1252.4	1254.2	1255.9	1256.8
160°	1273.6	1272.8	1271.3	1269.8	1268.2	1266.7	1268.2	1269.8	1271.3	1272.8	1273.6
162.5°	1289.4	1288.7	1287.4	1286.1	1284.8	1283.5	1284.8	1286.1	1287.4	1288.7	1289.4
165°	1303.2	1302.4	1300.9	1299.4	1297.8	1296.3	1297.8	1299.4	1300.9	1302.4	1303.2
167.5°	1314.1	1313.2	1311.5	1309.7	1308.0	1306.2	1308.0	1309.7	1311.5	1313.2	1314.1
170°	1323.0	1322.1	1320.4	1318.6	1316.9	1315.1	1316.9	1318.6	1320.4	1322.1	1323.0
172.5°	1328.9	1327.9	1325.9	1324.0	1322.0	1320.0	1322.0	1324.0	1325.9	1327.9	1328.9
175°	1332.9	1332.0	1330.3	1328.5	1326.8	1325.0	1326.8	1328.5	1330.3	1332.0	1332.9
177.5°	1335.8	1334.7	1332.5	1330.4	1328.2	1326.0	1328.2	1330.4	1332.5	1334.7	1335.8
180°	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9

TEST NUMBER: P1010970

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3	1229.3
2.5°	1163.0	1167.2	1163.0	1154.6	1163.0	1168.2	1173.5	1181.9	1186.1	1186.1	1192.5
5°	1096.7	1105.1	1101.9	1099.8	1108.3	1113.5	1121.9	1132.5	1144.0	1151.4	1159.8
7.5°	1037.7	1043.0	1048.3	1048.3	1056.7	1068.3	1080.9	1093.5	1108.3	1118.8	1125.1
10°	986.2	990.4	993.5	997.7	1010.4	1023.0	1039.8	1055.6	1068.3	1079.8	1090.4
12.5°	936.7	943.0	950.4	953.5	963.0	978.8	994.6	1013.5	1033.5	1045.1	1055.6
15°	889.3	892.5	900.9	910.4	918.8	935.6	955.6	975.6	992.5	1010.4	1019.8
17.5°	840.9	842.0	864.1	858.8	886.2	902.0	912.5	931.4	958.8	973.5	988.3
20°	793.6	804.1	813.6	818.8	833.6	851.5	882.0	896.7	918.8	932.5	945.1
22.5°	756.7	772.5	772.5	785.1	792.5	809.4	831.5	859.9	884.1	893.6	911.4
25°	724.1	731.5	744.1	748.3	762.0	776.7	791.5	822.0	848.3	860.9	873.6
27.5°	682.0	691.5	708.3	708.3	726.2	742.0	759.9	779.9	806.2	824.1	837.8
30°	649.4	658.8	666.2	677.8	685.2	699.9	731.5	746.2	769.4	785.1	802.0
32.5°	618.9	626.2	632.5	645.2	653.6	670.4	687.3	713.6	733.6	748.3	766.2
35°	585.2	592.5	601.0	610.4	623.1	638.9	654.6	676.7	696.7	710.4	725.2
37.5°	553.6	558.9	571.5	577.8	588.3	603.1	623.1	646.2	664.1	674.6	689.4
40°	523.1	527.3	536.8	548.3	555.7	567.3	588.3	608.3	630.4	643.1	654.6
42.5°	490.5	495.7	504.1	515.7	527.3	539.9	551.5	574.7	594.6	605.2	617.8
45°	462.0	465.2	471.5	483.1	494.7	504.1	522.0	543.1	562.0	570.4	584.1
47.5°	428.4	431.5	441.0	446.2	458.9	471.5	489.4	510.5	527.3	535.7	548.3
50°	393.6	396.8	403.1	414.7	423.1	436.8	452.6	470.5	491.5	503.1	510.5
52.5°	359.9	366.3	371.5	381.0	391.5	405.2	419.9	436.8	454.7	466.2	474.7
55°	326.3	331.5	337.8	343.1	355.7	368.4	385.2	401.0	416.8	427.3	436.8
57.5°	288.4	295.7	302.1	312.6	322.1	332.6	351.5	364.2	383.1	390.5	398.9
60°	255.8	263.1	268.4	276.8	285.2	298.9	311.5	327.3	343.1	352.6	363.1
62.5°	228.4	231.5	234.7	243.1	251.5	264.2	276.8	292.6	309.4	314.7	323.1
65°	201.0	204.2	209.4	216.8	223.1	230.5	244.2	256.8	272.6	281.0	284.2
67.5°	177.9	181.0	182.1	187.3	192.6	201.0	208.4	221.0	235.8	241.0	247.3
70°	151.6	156.8	157.9	162.1	164.2	169.4	177.9	187.3	198.9	208.4	213.7
72.5°	121.0	128.4	130.5	136.8	140.0	145.2	151.6	158.9	166.3	170.5	174.7
75°	98.9	101.0	102.1	107.4	112.6	120.0	123.1	127.3	133.7	138.9	143.1
77.5°	82.1	83.1	84.2	84.2	85.3	89.5	95.8	101.0	105.2	107.4	110.5
80°	66.3	65.3	65.3	66.3	66.3	66.3	68.4	75.8	77.9	83.1	82.1
82.5°	51.6	49.5	50.5	49.5	49.5	49.5	49.5	50.5	50.5	53.7	55.8
85°	33.7	34.7	33.7	33.7	32.6	33.7	32.6	32.6	31.6	31.6	30.5
87.5°	17.9	18.9	17.9	17.9	16.8	17.9	16.8	16.8	15.8	15.8	13.7
90°	27.3	26.4	25.5	24.6	23.7	20.9	18.0	15.2	12.3	10.9	9.8
92.5°	31.8	30.3	28.8	27.2	25.7	23.7	21.7	19.8	17.8	16.8	17.5
95°	36.7	35.2	33.7	32.1	30.6	28.2	25.8	23.4	21.0	19.8	24.3
97.5°	38.6	36.9	35.1	33.4	31.6	42.8	54.0	65.2	76.4	82.0	85.1
100°	39.6	37.9	36.1	34.4	32.6	66.8	101.1	135.3	169.6	186.7	184.5
102.5°	44.1	51.4	58.6	65.9	73.1	111.3	149.5	187.7	225.9	245.0	243.6
105°	60.9	99.8	138.7	177.5	216.4	236.2	255.9	275.7	295.4	305.3	304.1
107.5°	249.1	282.9	316.7	350.5	384.3	381.0	377.7	374.4	371.1	369.5	368.5
110°	416.6	423.9	431.1	438.4	445.6	443.2	440.8	438.3	435.9	434.7	433.8

TEST NUMBER: P1010970

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	515.7	513.8	511.8	509.9	507.9	505.5	503.1	500.6	498.2	497.0	496.2
115°	575.9	573.7	571.5	569.3	567.1	565.1	563.1	561.2	559.2	558.2	557.5
117.5°	632.4	630.7	628.9	627.2	625.4	624.3	623.2	622.1	621.0	620.5	619.7
120°	688.8	687.1	685.3	683.6	681.8	681.1	680.5	679.8	679.1	678.8	677.8
122.5°	742.5	741.4	740.3	739.2	738.1	737.2	736.3	735.4	734.5	734.1	733.3
125°	792.2	791.7	791.3	790.8	790.4	789.5	788.7	787.8	786.9	786.5	785.6
127.5°	845.5	844.8	844.1	843.5	842.8	841.7	840.6	839.5	838.4	837.9	837.0
130°	892.8	891.9	891.0	890.1	889.2	888.3	887.5	886.6	885.7	885.3	884.4
132.5°	937.3	936.4	935.5	934.6	933.7	933.0	932.4	931.7	931.0	930.7	929.8
135°	981.8	981.1	980.5	979.8	979.2	978.3	977.4	976.5	975.6	975.2	974.5
137.5°	1023.1	1022.0	1020.9	1019.8	1018.7	1018.3	1017.8	1017.4	1016.9	1016.7	1015.8
140°	1060.8	1059.9	1059.0	1058.1	1057.2	1056.5	1055.9	1055.2	1054.5	1054.2	1053.5
142.5°	1096.4	1095.7	1095.1	1094.4	1093.8	1093.1	1092.5	1091.8	1091.1	1090.8	1090.1
145°	1129.1	1128.7	1128.2	1127.8	1127.4	1127.0	1126.5	1126.1	1125.6	1125.4	1124.6
147.5°	1159.8	1159.3	1158.9	1158.4	1158.0	1157.6	1157.1	1156.7	1156.2	1156.0	1155.5
150°	1187.4	1187.0	1186.5	1186.1	1185.7	1185.3	1184.8	1184.4	1183.9	1183.7	1183.4
152.5°	1212.9	1212.0	1211.1	1210.3	1209.4	1209.2	1209.0	1208.7	1208.5	1208.4	1208.3
155°	1235.5	1234.4	1233.3	1232.2	1231.1	1230.9	1230.7	1230.4	1230.2	1230.1	1230.3
157.5°	1256.1	1254.8	1253.5	1252.2	1250.9	1251.1	1251.3	1251.6	1251.8	1251.9	1251.9
160°	1272.9	1271.6	1270.3	1269.0	1267.7	1267.9	1268.1	1268.4	1268.6	1268.7	1268.8
162.5°	1288.6	1287.1	1285.6	1284.0	1282.5	1282.7	1282.9	1283.2	1283.4	1283.5	1283.8
165°	1302.3	1300.6	1298.8	1297.1	1295.3	1295.5	1295.7	1296.0	1296.2	1296.3	1296.6
167.5°	1313.2	1311.5	1309.7	1308.0	1306.2	1306.2	1306.2	1306.2	1306.2	1306.2	1306.6
170°	1322.1	1320.4	1318.6	1316.9	1315.1	1315.1	1315.1	1315.1	1315.1	1315.1	1315.5
172.5°	1328.0	1326.3	1324.5	1322.8	1321.0	1320.8	1320.6	1320.3	1320.1	1320.0	1320.6
175°	1332.1	1330.6	1329.1	1327.5	1326.0	1325.8	1325.6	1325.3	1325.1	1325.0	1325.5
177.5°	1334.9	1333.2	1331.4	1329.7	1327.9	1327.7	1327.5	1327.2	1327.0	1326.9	1327.5
180°	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9

TEST NUMBER: P1010970

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1229.3	1229.3	1229.3	1229.3
2.5°	1197.7	1205.1	1219.8	1232.4
5°	1172.5	1184.0	1206.1	1228.2
7.5°	1141.9	1159.8	1188.2	1218.8
10°	1112.5	1135.6	1170.4	1206.1
12.5°	1083.0	1107.2	1144.0	1190.3
15°	1048.3	1073.5	1117.7	1173.5
17.5°	1017.7	1051.4	1091.4	1147.2
20°	985.1	1010.4	1061.9	1120.9
22.5°	944.1	986.2	1034.6	1096.7
25°	911.4	948.3	996.7	1067.2
27.5°	871.4	914.6	973.5	1035.6
30°	838.8	874.6	929.3	1004.1
32.5°	800.9	843.0	899.9	973.5
35°	767.3	803.0	856.7	931.4
37.5°	727.3	766.2	826.2	892.5
40°	692.5	730.4	787.3	849.3
42.5°	650.4	690.4	747.3	799.9
45°	616.7	653.6	698.8	747.3
47.5°	575.7	614.6	658.8	692.5
50°	538.9	574.7	609.4	637.8
52.5°	498.9	531.5	563.1	584.1
55°	462.0	487.3	512.6	527.3
57.5°	418.9	443.1	464.1	472.6
60°	381.0	401.0	414.7	424.1
62.5°	341.0	355.7	366.3	371.5
65°	302.1	312.6	317.8	323.1
67.5°	262.1	271.5	274.7	281.0
70°	220.0	230.5	232.6	235.8
72.5°	188.4	188.4	192.6	196.8
75°	150.5	152.6	154.7	154.7
77.5°	117.9	117.9	120.0	121.0
80°	86.3	87.4	87.4	86.3
82.5°	58.9	61.0	58.9	57.9
85°	32.6	36.8	34.7	34.7
87.5°	13.7	13.7	15.8	13.7
90°	7.6	5.4	3.2	1.0
92.5°	18.8	20.1	21.4	22.7
95°	33.3	42.3	51.3	60.3
97.5°	91.2	97.4	103.5	109.7
100°	180.1	175.8	171.4	167.0
102.5°	240.7	237.9	235.0	232.2
105°	301.7	299.2	296.8	294.4
107.5°	366.5	364.6	362.6	360.6
110°	432.1	430.3	428.6	426.8

TEST NUMBER: P1010970

CATALOG NUMBER: S123RDIP-B775D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	494.7	493.2	491.6	490.1
115°	556.2	554.9	553.6	552.3
117.5°	618.2	616.7	615.1	613.6
120°	675.8	673.9	671.9	669.9
122.5°	731.8	730.3	728.7	727.2
125°	783.9	782.1	780.4	778.6
127.5°	835.3	833.5	831.8	830.0
130°	882.7	880.9	879.2	877.4
132.5°	928.1	926.3	924.6	922.8
135°	973.2	971.9	970.6	969.3
137.5°	1014.1	1012.3	1010.6	1008.8
140°	1052.2	1050.9	1049.6	1048.3
142.5°	1088.8	1087.5	1086.2	1084.9
145°	1123.1	1121.6	1120.0	1118.5
147.5°	1154.4	1153.3	1152.2	1151.1
150°	1182.7	1182.0	1181.4	1180.7
152.5°	1208.1	1207.8	1207.6	1207.4
155°	1230.8	1231.2	1231.7	1232.1
157.5°	1251.9	1251.9	1251.9	1251.9
160°	1269.0	1269.2	1269.4	1269.6
162.5°	1284.5	1285.1	1285.8	1286.4
165°	1297.3	1298.0	1298.6	1299.3
167.5°	1307.5	1308.4	1309.2	1310.1
170°	1316.4	1317.3	1318.1	1319.0
172.5°	1321.7	1322.8	1323.9	1325.0
175°	1326.6	1327.7	1328.8	1329.9
177.5°	1328.6	1329.7	1330.8	1331.9
180°	1329.9	1329.9	1329.9	1329.9

(END OF REPORT)