

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010982

Luminaire Tested: S123RDIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010982
REPORT IS A COMBINATION OF REPORTS P993568 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B775D1195UB2750-4F0-XX-W2A-A_4000K
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7784.0 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010982

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010982

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46
1	96	92	88	85	87	84	81	78	68	66	64	54	53	52	41	41	40
2	88	81	75	70	79	74	69	65	60	57	54	48	46	44	37	36	34
3	80	71	64	59	73	65	59	54	54	49	46	43	40	38	33	31	30
4	74	63	56	50	67	58	51	46	48	43	39	39	35	33	30	28	26
5	68	57	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20
7	58	46	38	33	52	42	36	31	35	30	26	29	25	22	23	20	18
8	54	42	34	29	49	38	32	27	32	27	24	26	23	20	21	18	16
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	19	17	15
10	47	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13159	13159	13159	13159
5°	13168	15155	13203	11244
10°	13052	18294	13110	9821
15°	12918	20763	12918	8659
20°	12653	22396	12724	7681
25°	12459	21277	12435	7009
30°	12234	14742	12208	6351
35°	11962	9466	11908	5855
40°	11624	6684	11566	5362
45°	11036	5349	11021	4882
50°	10314	4475	10280	4321
55°	9502	3688	9426	3663
60°	8704	3048	8617	3114
65°	7767	2439	7818	2640
70°	6903	1694	7088	2134
75°	5854	1258	6090	1642
80°	4658	834	5054	1231
85°	3314	395	3621	765

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 17567 cd/sqm

TEST NUMBER: P1010982

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.1	1.5
10°-20°	375.8	4.8
20°-30°	591.9	7.6
30°-40°	615.5	7.9
40°-50°	526.5	6.8
50°-60°	401.4	5.2
60°-70°	257.2	3.3
70°-80°	123.2	1.6
80°-90°	35.5	0.5
90°-100°	54.8	0.7
100°-110°	264.9	3.4
110°-120°	649.2	8.3
120°-130°	824.1	10.6
130°-140°	880.4	11.3
140°-150°	823.3	10.6
150°-160°	664.0	8.5
160°-170°	428.5	5.5
170°-180°	147.7	1.9
0°-30°	1087.7	14.0
0°-40°	1703.2	21.9
0°-60°	2631.2	33.8
0°-90°	3047.1	39.1
90°-120°	968.9	12.4
90°-150°	3496.7	44.9
90°-180°	4737.0	60.9
0°-180°	7784.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1222	1222	1222	1222	1222	
5°	1221	1452	1225	1077	1221	116
15°	1167	2063	1167	860	1167	328
25°	1061	2126	1059	700	1061	489
35°	926	922	922	570	926	580
45°	743	492	742	449	743	572
55°	524	309	520	307	524	470
65°	321	178	323	193	321	321
75°	154	75	160	98	154	166
85°	34	18	38	34	34	39
90°	1	35	1	35	1	6
95°	70	44	70	44	70	84
105°	344	51	344	51	344	365
115°	645	679	645	679	645	637
125°	910	928	910	928	910	813
135°	1132	1144	1132	1144	1132	872
145°	1307	1320	1307	1320	1307	818
155°	1440	1437	1440	1437	1440	663
165°	1518	1515	1518	1515	1518	429
175°	1554	1548	1554	1548	1554	148
180°	1554	1554	1554	1554	1554	

TEST NUMBER: P1010982

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5
2.5°	1225.6	1234.0	1240.3	1244.4	1254.9	1261.2	1266.4	1275.8	1275.8	1277.9	1282.1
5°	1221.4	1239.2	1251.8	1268.5	1290.5	1301.0	1315.6	1328.2	1346.0	1355.4	1364.8
7.5°	1212.0	1237.1	1263.3	1288.4	1320.8	1341.8	1356.4	1388.9	1411.9	1440.2	1462.1
10°	1199.4	1234.0	1267.5	1306.2	1350.2	1381.6	1403.5	1446.4	1490.4	1530.2	1563.7
12.5°	1183.7	1225.6	1273.7	1320.8	1382.6	1414.0	1449.6	1503.0	1565.8	1616.0	1661.0
15°	1167.0	1215.1	1269.6	1327.1	1404.6	1448.5	1499.8	1564.7	1634.8	1707.1	1768.8
17.5°	1140.8	1201.5	1262.2	1346.0	1437.0	1463.2	1507.1	1596.1	1683.0	1747.9	1823.2
20°	1114.7	1182.7	1259.1	1334.5	1432.8	1493.5	1534.4	1628.6	1721.7	1800.2	1872.4
22.5°	1090.6	1161.8	1241.3	1336.5	1428.6	1489.4	1540.6	1639.0	1746.8	1834.7	1923.7
25°	1061.3	1138.7	1226.6	1316.7	1428.6	1474.7	1531.2	1645.3	1759.4	1860.9	1970.8
27.5°	1029.9	1108.4	1195.3	1287.4	1389.9	1458.0	1513.4	1635.9	1775.1	1883.9	1997.0
30°	998.5	1079.1	1162.8	1245.5	1360.6	1425.5	1489.4	1624.4	1783.5	1908.0	1994.9
32.5°	968.1	1036.2	1118.8	1199.4	1313.5	1384.7	1456.9	1612.9	1786.6	1891.3	1933.1
35°	926.3	997.4	1064.4	1150.2	1265.4	1335.5	1420.3	1611.8	1773.0	1837.9	1816.9
37.5°	887.5	947.2	1011.0	1087.4	1205.7	1296.8	1384.7	1584.6	1728.0	1732.2	1613.9
40°	844.6	893.8	947.2	1027.8	1155.5	1245.5	1340.7	1542.7	1646.3	1584.6	1376.3
42.5°	795.4	839.4	881.3	959.8	1099.0	1199.4	1302.0	1490.4	1528.1	1385.7	1169.1
45°	743.1	778.7	817.4	900.1	1039.3	1138.7	1241.3	1409.8	1371.1	1170.1	963.9
47.5°	688.7	719.0	756.7	832.1	975.5	1077.0	1174.3	1294.7	1196.3	980.7	808.0
50°	634.3	658.3	695.0	772.4	910.6	1002.7	1092.7	1171.2	1033.0	841.5	667.7
52.5°	580.9	599.7	637.4	703.3	837.3	925.2	990.1	1020.5	880.2	695.0	579.8
55°	524.4	545.3	570.4	637.4	770.3	835.2	878.1	877.1	732.6	589.3	479.4
57.5°	469.9	488.8	510.8	577.7	685.5	729.5	766.1	748.3	611.2	482.5	411.3
60°	421.8	432.3	456.3	512.8	594.5	632.2	653.1	622.7	499.2	407.1	340.2
62.5°	369.5	379.9	399.8	453.2	503.4	523.3	541.1	502.4	412.4	331.8	291.0
65°	321.3	334.9	347.5	390.4	417.6	441.7	439.6	407.1	322.4	270.0	236.5
67.5°	279.4	284.7	295.1	321.3	333.9	351.7	352.7	316.1	259.6	219.8	199.9
70°	234.4	239.7	247.0	259.6	267.9	272.1	270.0	237.6	195.7	171.6	153.9
72.5°	195.7	194.7	199.9	199.9	208.3	207.2	201.0	175.8	148.6	128.7	118.3
75°	153.9	154.9	155.9	153.9	150.7	146.5	141.3	122.5	104.7	95.2	85.8
77.5°	120.4	118.3	119.3	112.0	107.8	103.6	96.3	86.9	72.2	70.1	65.9
80°	85.8	84.8	83.7	80.6	71.2	67.0	61.8	56.5	53.4	51.3	50.2
82.5°	57.6	57.6	55.5	49.2	44.0	40.8	39.8	37.7	34.5	34.5	33.5
85°	34.5	33.5	31.4	25.1	22.0	22.0	22.0	22.0	19.9	19.9	18.8
87.5°	13.6	12.6	9.4	9.4	8.4	8.4	8.4	7.3	7.3	6.3	6.3
90°	1.2	3.8	6.3	8.9	11.4	12.7	14.4	17.7	21.0	24.4	27.7
92.5°	26.6	25.0	23.5	21.9	20.4	19.6	20.8	23.1	25.4	27.7	30.0
95°	70.4	59.9	49.4	38.9	28.4	23.1	24.5	27.3	30.2	33.0	35.8
97.5°	128.1	120.9	113.7	106.6	99.4	95.8	89.3	76.2	63.1	50.0	36.9
100°	195.1	200.2	205.4	210.5	215.6	218.2	198.2	158.2	118.1	78.1	38.1
102.5°	271.3	274.6	278.0	281.3	284.6	286.3	264.0	219.3	174.7	130.0	85.4
105°	344.0	346.8	349.6	352.5	355.3	356.7	345.2	322.1	299.0	275.9	252.8
107.5°	421.4	423.7	426.0	428.3	430.6	431.7	433.6	437.5	441.4	445.2	449.1
110°	498.7	500.7	502.8	504.8	506.9	507.9	509.3	512.1	515.0	517.8	520.6

TEST NUMBER: P1010982

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	572.6	574.4	576.2	578.0	579.8	580.7	582.1	584.9	587.8	590.6	593.4
115°	645.3	646.8	648.4	649.9	651.4	652.2	653.4	655.7	658.0	660.3	662.6
117.5°	716.9	718.7	720.5	722.3	724.1	725.0	725.6	726.9	728.2	729.4	730.7
120°	782.7	785.0	787.3	789.6	791.9	793.1	793.5	794.2	795.0	795.7	796.5
122.5°	849.6	851.4	853.2	855.0	856.8	857.7	858.2	859.2	860.3	861.3	862.3
125°	909.7	911.7	913.8	915.8	917.9	918.9	919.4	920.4	921.5	922.5	923.5
127.5°	969.7	971.7	973.8	975.8	977.9	978.9	979.5	980.8	982.1	983.4	984.7
130°	1025.1	1027.1	1029.2	1031.2	1033.3	1034.3	1034.8	1035.8	1036.9	1037.9	1038.9
132.5°	1078.2	1080.2	1082.3	1084.3	1086.4	1087.4	1087.8	1088.6	1089.3	1090.1	1090.9
135°	1132.5	1134.0	1135.6	1137.1	1138.6	1139.4	1139.9	1140.9	1142.0	1143.0	1144.0
137.5°	1178.6	1180.7	1182.7	1184.8	1186.9	1187.9	1188.2	1188.7	1189.2	1189.7	1190.2
140°	1224.8	1226.3	1227.9	1229.4	1230.9	1231.7	1232.1	1232.9	1233.6	1234.4	1235.2
142.5°	1267.5	1269.0	1270.6	1272.1	1273.6	1274.4	1274.8	1275.6	1276.3	1277.1	1277.9
145°	1306.8	1308.6	1310.4	1312.1	1313.9	1314.8	1315.1	1315.6	1316.1	1316.7	1317.2
147.5°	1344.9	1346.2	1347.4	1348.7	1350.0	1350.6	1350.9	1351.4	1351.9	1352.4	1352.9
150°	1379.5	1380.3	1381.1	1381.8	1382.6	1383.0	1383.3	1383.8	1384.3	1384.8	1385.3
152.5°	1410.7	1410.9	1411.2	1411.4	1411.7	1411.8	1411.9	1412.2	1412.5	1412.7	1413.0
155°	1439.5	1439.0	1438.5	1438.0	1437.5	1437.2	1437.3	1437.6	1437.9	1438.1	1438.4
157.5°	1462.6	1462.6	1462.6	1462.6	1462.6	1462.6	1462.5	1462.2	1462.0	1461.7	1461.5
160°	1483.4	1483.1	1482.9	1482.6	1482.3	1482.2	1482.1	1481.8	1481.6	1481.3	1481.1
162.5°	1503.0	1502.2	1501.4	1500.7	1499.9	1499.5	1499.4	1499.1	1498.9	1498.6	1498.4
165°	1518.0	1517.2	1516.5	1515.7	1515.0	1514.6	1514.5	1514.2	1513.9	1513.7	1513.4
167.5°	1530.7	1529.7	1528.7	1527.6	1526.6	1526.1	1526.1	1526.1	1526.1	1526.1	1526.1
170°	1541.1	1540.1	1539.1	1538.0	1537.0	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5
172.5°	1548.0	1546.7	1545.5	1544.2	1542.9	1542.3	1542.4	1542.7	1542.9	1543.2	1543.4
175°	1553.8	1552.5	1551.2	1549.9	1548.6	1548.0	1548.1	1548.4	1548.7	1548.9	1549.2
177.5°	1556.1	1554.8	1553.5	1552.2	1550.9	1550.3	1550.4	1550.7	1551.0	1551.2	1551.5
180°	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8

TEST NUMBER: P1010982

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5
2.5°	1290.5	1290.5	1299.9	1309.3	1304.1	1307.2	1318.8	1314.6	1322.9	1321.9	1325.0
5°	1387.8	1399.3	1408.8	1428.6	1431.8	1428.6	1448.5	1453.8	1463.2	1451.7	1456.9
7.5°	1497.7	1521.8	1544.8	1574.1	1583.5	1585.6	1596.1	1610.8	1623.3	1600.3	1611.8
10°	1604.5	1641.1	1688.2	1714.4	1737.4	1745.8	1754.2	1763.6	1778.2	1791.8	1781.4
12.5°	1719.6	1773.0	1818.0	1865.1	1893.4	1890.2	1914.3	1920.6	1932.1	1935.2	1939.4
15°	1813.8	1889.2	1917.4	1987.5	1993.8	2014.8	2042.0	2066.0	2069.2	2062.9	2062.9
17.5°	1903.8	1968.7	2018.9	2075.5	2087.0	2104.8	2139.3	2150.8	2155.0	2154.0	2154.0
20°	1977.1	2020.0	2104.8	2151.9	2170.7	2193.7	2217.8	2232.5	2235.6	2239.8	2233.5
22.5°	2025.2	2090.1	2159.2	2197.9	2213.6	2222.0	2237.7	2241.9	2236.6	2237.7	2238.7
25°	2062.9	2126.8	2168.6	2179.1	2178.0	2167.6	2156.1	2136.2	2134.1	2125.7	2109.0
27.5°	2073.4	2097.4	2092.2	2049.3	2006.4	2002.2	1933.1	1895.4	1852.5	1858.8	1834.7
30°	2016.9	1985.5	1911.1	1802.3	1757.3	1684.0	1606.6	1526.0	1494.6	1460.0	1523.9
32.5°	1878.7	1766.7	1634.8	1493.5	1418.2	1353.3	1270.6	1212.0	1178.5	1150.2	1204.7
35°	1670.4	1495.6	1320.8	1186.9	1125.1	1066.5	989.1	959.8	917.9	922.1	927.3
37.5°	1402.5	1209.9	1078.0	946.2	905.3	881.3	824.7	779.7	765.1	760.9	760.9
40°	1151.3	993.3	876.0	772.4	741.0	721.1	676.1	655.2	639.5	635.3	640.5
42.5°	952.4	817.4	726.4	657.3	635.3	610.2	591.3	565.2	562.0	554.7	564.1
45°	799.6	682.4	614.4	564.1	545.3	535.9	514.9	499.2	493.0	491.9	499.2
47.5°	678.2	587.2	527.5	496.1	481.4	472.0	454.2	448.0	441.7	443.8	440.6
50°	569.4	501.3	462.6	434.4	424.9	415.5	404.0	397.7	394.6	394.6	393.5
52.5°	488.8	432.3	407.1	381.0	376.8	371.6	359.0	354.8	349.6	348.5	352.7
55°	418.7	379.9	354.8	339.1	334.9	324.5	319.2	314.0	310.8	308.8	309.8
57.5°	357.9	328.6	311.9	298.3	291.0	286.8	277.4	276.3	274.2	274.2	273.2
60°	307.7	286.8	266.9	258.5	253.3	248.1	247.0	240.7	237.6	239.7	238.6
62.5°	260.6	243.9	232.4	222.9	219.8	215.6	212.5	210.4	207.2	208.3	208.3
65°	217.7	204.1	195.7	187.3	186.3	182.1	181.1	179.0	179.0	177.9	180.0
67.5°	179.0	169.6	162.2	157.0	153.9	154.9	150.7	147.6	147.6	146.5	149.7
70°	142.3	137.1	129.8	123.5	119.3	119.3	114.1	113.0	113.0	113.0	112.0
72.5°	109.9	100.5	97.3	95.2	95.2	95.2	93.1	93.1	92.1	93.1	92.1
75°	81.6	80.6	78.5	77.5	77.5	76.4	75.4	75.4	75.4	75.4	75.4
77.5°	63.8	63.8	61.8	60.7	60.7	60.7	59.7	59.7	58.6	58.6	58.6
80°	47.1	47.1	45.0	45.0	45.0	44.0	44.0	44.0	45.0	44.0	44.0
82.5°	32.4	32.4	31.4	32.4	31.4	30.4	30.4	30.4	29.3	30.4	30.4
85°	18.8	18.8	17.8	16.7	17.8	17.8	16.7	17.8	16.7	17.8	16.7
87.5°	7.3	6.3	6.3	6.3	5.2	6.3	5.2	5.2	6.3	5.2	6.3
90°	28.7	29.7	30.8	31.8	32.3	32.6	33.1	33.6	34.1	34.6	34.1
92.5°	31.8	33.6	35.4	37.2	38.1	38.2	38.5	38.7	39.0	39.2	39.0
95°	37.6	39.4	41.2	43.0	43.9	43.9	43.9	43.9	43.9	43.9	43.9
97.5°	39.0	41.0	43.1	45.2	46.2	46.3	46.6	46.8	47.1	47.3	47.1
100°	40.1	42.2	44.2	46.3	47.3	47.4	47.7	48.0	48.2	48.5	48.2
102.5°	76.9	68.5	60.0	51.5	47.3	47.6	48.1	48.6	49.1	49.6	49.1
105°	207.4	162.0	116.6	71.2	48.5	48.8	49.3	49.8	50.3	50.8	50.3
107.5°	409.6	370.1	330.6	291.1	271.3	254.5	220.9	187.3	153.7	120.1	153.7
110°	512.1	503.7	495.2	486.7	482.5	464.2	427.5	390.8	354.2	317.5	354.2

TEST NUMBER: P1010982

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	595.7	598.0	600.3	602.6	603.7	603.4	602.9	602.4	601.9	601.4	601.9
115°	665.2	667.8	670.3	672.9	674.2	674.7	675.7	676.8	677.8	678.8	677.8
117.5°	732.8	734.8	736.9	739.0	740.0	740.1	740.4	740.6	740.9	741.1	740.9
120°	798.6	800.6	802.7	804.8	805.8	805.8	805.8	805.8	805.8	805.8	805.8
122.5°	863.6	864.9	866.2	867.5	868.1	868.2	868.5	868.8	869.0	869.3	869.0
125°	924.0	924.5	925.0	925.5	925.8	926.1	926.6	927.1	927.6	928.1	927.6
127.5°	985.5	986.3	987.0	987.8	988.2	987.9	987.4	986.9	986.3	985.8	986.3
130°	1039.9	1041.0	1042.0	1043.1	1043.6	1043.3	1042.8	1042.3	1041.8	1041.3	1041.8
132.5°	1091.9	1092.9	1094.0	1095.0	1095.5	1095.1	1094.3	1093.6	1092.8	1092.0	1092.8
135°	1144.8	1145.6	1146.3	1147.1	1147.5	1147.1	1146.3	1145.6	1144.8	1144.0	1144.8
137.5°	1191.5	1192.7	1194.0	1195.3	1195.9	1195.6	1195.1	1194.6	1194.1	1193.6	1194.1
140°	1236.2	1237.2	1238.3	1239.3	1239.8	1239.5	1239.0	1238.5	1238.0	1237.5	1238.0
142.5°	1278.7	1279.5	1280.2	1281.0	1281.4	1281.0	1280.2	1279.5	1278.7	1277.9	1278.7
145°	1317.7	1318.2	1318.7	1319.2	1319.5	1319.5	1319.5	1319.5	1319.5	1319.5	1319.5
147.5°	1353.4	1353.9	1354.4	1354.9	1355.2	1354.6	1353.3	1352.0	1350.8	1349.5	1350.8
150°	1385.8	1386.3	1386.8	1387.3	1387.6	1387.2	1386.4	1385.7	1384.9	1384.1	1384.9
152.5°	1414.0	1415.0	1416.1	1417.1	1417.6	1417.0	1415.7	1414.4	1413.1	1411.8	1413.1
155°	1439.7	1440.9	1442.2	1443.5	1444.1	1443.3	1441.8	1440.3	1438.7	1437.2	1438.7
157.5°	1463.0	1464.6	1466.1	1467.6	1468.4	1467.4	1465.3	1463.2	1461.2	1459.1	1461.2
160°	1482.6	1484.2	1485.7	1487.2	1488.0	1487.1	1485.3	1483.5	1481.7	1479.9	1481.7
162.5°	1500.2	1502.0	1503.8	1505.6	1506.5	1505.7	1504.2	1502.6	1501.1	1499.5	1501.1
165°	1515.4	1517.5	1519.5	1521.6	1522.6	1521.7	1519.9	1518.2	1516.4	1514.6	1516.4
167.5°	1528.1	1530.2	1532.2	1534.3	1535.3	1534.3	1532.2	1530.2	1528.1	1526.1	1528.1
170°	1538.5	1540.6	1542.6	1544.7	1545.7	1544.7	1542.6	1540.6	1538.5	1536.5	1538.5
172.5°	1545.4	1547.5	1549.5	1551.6	1552.6	1551.5	1549.2	1546.9	1544.6	1542.3	1544.6
175°	1551.0	1552.8	1554.6	1556.4	1557.3	1556.3	1554.2	1552.1	1550.1	1548.0	1550.1
177.5°	1553.5	1555.6	1557.6	1559.7	1560.7	1559.4	1556.9	1554.3	1551.8	1549.2	1551.8
180°	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8

TEST NUMBER: P1010982

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5
2.5°	1319.8	1313.5	1309.3	1306.2	1303.1	1312.5	1299.9	1286.3	1276.9	1270.6	1268.5
5°	1458.0	1444.3	1432.8	1423.4	1425.5	1425.5	1403.5	1379.5	1358.5	1347.0	1334.5
7.5°	1618.1	1603.4	1580.4	1575.2	1571.0	1544.8	1522.8	1478.9	1452.7	1426.6	1403.5
10°	1777.2	1758.3	1736.4	1729.0	1718.6	1686.1	1652.6	1596.1	1563.7	1515.5	1485.2
12.5°	1925.8	1902.8	1880.8	1875.6	1859.9	1831.6	1774.0	1715.4	1660.0	1608.7	1555.3
15°	2050.3	2044.1	2010.6	1989.6	1955.1	1916.4	1903.8	1824.3	1754.2	1700.8	1604.5
17.5°	2155.0	2125.7	2094.3	2080.7	2067.1	2022.1	1977.1	1895.4	1820.1	1741.6	1679.8
20°	2238.7	2206.3	2184.3	2164.4	2158.1	2106.9	2035.7	1963.5	1880.8	1792.9	1712.3
22.5°	2242.9	2238.7	2224.1	2212.6	2200.0	2166.5	2110.0	2020.0	1932.1	1835.8	1730.1
25°	2156.1	2149.8	2191.6	2181.2	2189.5	2177.0	2146.6	2071.3	1968.7	1855.7	1748.9
27.5°	1894.4	1958.2	2024.2	2047.2	2062.9	2107.9	2122.6	2080.7	1998.0	1877.7	1758.3
30°	1538.5	1623.3	1730.1	1787.6	1831.6	1915.3	2024.2	2037.8	1999.1	1902.8	1756.2
32.5°	1207.8	1285.3	1371.1	1439.1	1497.7	1669.4	1815.9	1921.6	1940.5	1890.2	1761.5
35°	973.4	1006.9	1088.5	1153.4	1232.9	1379.5	1552.2	1722.8	1837.9	1844.2	1745.8
37.5°	802.8	820.6	891.7	928.4	975.5	1104.2	1265.4	1488.3	1667.3	1752.1	1701.8
40°	664.6	705.4	746.2	767.2	800.7	889.6	1044.5	1219.3	1441.2	1598.2	1633.8
42.5°	576.7	594.5	620.7	650.0	670.9	748.3	852.0	1012.1	1212.0	1430.7	1529.1
45°	508.7	514.9	542.2	561.0	583.0	637.4	710.7	844.6	1020.5	1236.1	1403.5
47.5°	452.1	464.7	479.4	490.9	505.5	547.4	610.2	707.5	862.4	1055.0	1235.0
50°	401.9	409.2	428.1	433.3	443.8	473.1	521.2	595.5	723.2	877.1	1063.4
52.5°	354.8	368.4	375.7	383.1	392.5	416.6	448.0	508.7	605.0	749.4	907.4
55°	318.2	322.4	332.8	339.1	346.4	363.2	390.4	435.4	510.8	625.9	775.6
57.5°	282.6	282.6	293.1	298.3	305.6	318.2	342.2	376.8	431.2	517.0	654.1
60°	244.9	246.0	254.3	260.6	262.7	275.3	295.1	322.4	364.2	427.0	539.0
62.5°	211.4	216.7	220.8	222.9	230.3	237.6	254.3	273.2	302.5	357.9	437.5
65°	183.2	184.2	187.3	189.4	192.6	201.0	213.5	226.1	251.2	292.0	356.9
67.5°	150.7	154.9	159.1	159.1	162.2	166.4	179.0	189.4	208.3	232.4	276.3
70°	113.0	115.1	121.4	124.5	128.7	136.1	142.3	148.6	163.3	181.1	214.6
72.5°	94.2	94.2	96.3	97.3	97.3	102.6	112.0	118.3	125.6	138.2	161.2
75°	75.4	75.4	78.5	77.5	79.5	81.6	82.7	86.9	91.1	100.5	114.1
77.5°	59.7	60.7	60.7	61.8	61.8	62.8	63.8	65.9	68.0	73.3	79.5
80°	44.0	45.0	45.0	46.1	46.1	47.1	48.1	49.2	51.3	53.4	56.5
82.5°	30.4	31.4	31.4	32.4	31.4	32.4	33.5	33.5	34.5	36.6	37.7
85°	17.8	17.8	18.8	17.8	17.8	17.8	18.8	18.8	19.9	23.0	23.0
87.5°	5.2	6.3	5.2	6.3	6.3	6.3	6.3	7.3	7.3	8.4	9.4
90°	33.6	33.1	32.6	32.3	31.8	30.8	29.7	28.7	27.7	24.4	21.0
92.5°	38.7	38.5	38.2	38.1	37.2	35.4	33.6	31.8	30.0	27.7	25.4
95°	43.9	43.9	43.9	43.9	43.0	41.2	39.4	37.6	35.8	33.0	30.2
97.5°	46.8	46.6	46.3	46.2	45.2	43.1	41.0	39.0	36.9	50.0	63.1
100°	48.0	47.7	47.4	47.3	46.3	44.2	42.2	40.1	38.1	78.1	118.1
102.5°	48.6	48.1	47.6	47.3	51.5	60.0	68.5	76.9	85.4	130.0	174.7
105°	49.8	49.3	48.8	48.5	71.2	116.6	162.0	207.4	252.8	275.9	299.0
107.5°	187.3	220.9	254.5	271.3	291.1	330.6	370.1	409.6	449.1	445.2	441.4
110°	390.8	427.5	464.2	482.5	486.7	495.2	503.7	512.1	520.6	517.8	515.0

TEST NUMBER: P1010982

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	602.4	602.9	603.4	603.7	602.6	600.3	598.0	595.7	593.4	590.6	587.8
115°	676.8	675.7	674.7	674.2	672.9	670.3	667.8	665.2	662.6	660.3	658.0
117.5°	740.6	740.4	740.1	740.0	739.0	736.9	734.8	732.8	730.7	729.4	728.2
120°	805.8	805.8	805.8	805.8	804.8	802.7	800.6	798.6	796.5	795.7	795.0
122.5°	868.8	868.5	868.2	868.1	867.5	866.2	864.9	863.6	862.3	861.3	860.3
125°	927.1	926.6	926.1	925.8	925.5	925.0	924.5	924.0	923.5	922.5	921.5
127.5°	986.9	987.4	987.9	988.2	987.8	987.0	986.3	985.5	984.7	983.4	982.1
130°	1042.3	1042.8	1043.3	1043.6	1043.1	1042.0	1041.0	1039.9	1038.9	1037.9	1036.9
132.5°	1093.6	1094.3	1095.1	1095.5	1095.0	1094.0	1092.9	1091.9	1090.9	1090.1	1089.3
135°	1145.6	1146.3	1147.1	1147.5	1147.1	1146.3	1145.6	1144.8	1144.0	1143.0	1142.0
137.5°	1194.6	1195.1	1195.6	1195.9	1195.3	1194.0	1192.7	1191.5	1190.2	1189.7	1189.2
140°	1238.5	1239.0	1239.5	1239.8	1239.3	1238.3	1237.2	1236.2	1235.2	1234.4	1233.6
142.5°	1279.5	1280.2	1281.0	1281.4	1281.0	1280.2	1279.5	1278.7	1277.9	1277.1	1276.3
145°	1319.5	1319.5	1319.5	1319.5	1319.2	1318.7	1318.2	1317.7	1317.2	1316.7	1316.1
147.5°	1352.0	1353.3	1354.6	1355.2	1354.9	1354.4	1353.9	1353.4	1352.9	1352.4	1351.9
150°	1385.7	1386.4	1387.2	1387.6	1387.3	1386.8	1386.3	1385.8	1385.3	1384.8	1384.3
152.5°	1414.4	1415.7	1417.0	1417.6	1417.1	1416.1	1415.0	1414.0	1413.0	1412.7	1412.5
155°	1440.3	1441.8	1443.3	1444.1	1443.5	1442.2	1440.9	1439.7	1438.4	1438.1	1437.9
157.5°	1463.2	1465.3	1467.4	1468.4	1467.6	1466.1	1464.6	1463.0	1461.5	1461.7	1462.0
160°	1483.5	1485.3	1487.1	1488.0	1487.2	1485.7	1484.2	1482.6	1481.1	1481.3	1481.6
162.5°	1502.6	1504.2	1505.7	1506.5	1505.6	1503.8	1502.0	1500.2	1498.4	1498.6	1498.9
165°	1518.2	1519.9	1521.7	1522.6	1521.6	1519.5	1517.5	1515.4	1513.4	1513.7	1513.9
167.5°	1530.2	1532.2	1534.3	1535.3	1534.3	1532.2	1530.2	1528.1	1526.1	1526.1	1526.1
170°	1540.6	1542.6	1544.7	1545.7	1544.7	1542.6	1540.6	1538.5	1536.5	1536.5	1536.5
172.5°	1546.9	1549.2	1551.5	1552.6	1551.6	1549.5	1547.5	1545.4	1543.4	1543.2	1542.9
175°	1552.1	1554.2	1556.3	1557.3	1556.4	1554.6	1552.8	1551.0	1549.2	1548.9	1548.7
177.5°	1554.3	1556.9	1559.4	1560.7	1559.7	1557.6	1555.6	1553.5	1551.5	1551.2	1551.0
180°	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8

TEST NUMBER: P1010982

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5
2.5°	1265.4	1260.1	1254.9	1254.9	1243.4	1232.9	1227.7	1229.8	1223.5	1215.1	1206.8
5°	1320.8	1299.9	1295.7	1284.2	1268.5	1246.5	1235.0	1224.6	1212.0	1195.3	1179.6
7.5°	1372.1	1344.9	1330.3	1318.8	1288.4	1258.0	1232.9	1216.2	1194.2	1169.1	1150.2
10°	1439.1	1388.9	1373.2	1347.0	1304.1	1261.2	1231.9	1204.7	1174.3	1145.0	1119.9
12.5°	1492.5	1434.9	1405.6	1379.5	1324.0	1269.6	1220.4	1186.9	1150.2	1117.8	1085.4
15°	1553.2	1488.3	1437.0	1405.6	1335.5	1269.6	1214.1	1167.0	1126.2	1086.4	1058.1
17.5°	1582.5	1500.9	1477.8	1432.8	1331.3	1265.4	1197.3	1147.1	1097.9	1051.9	1018.4
20°	1628.6	1533.3	1475.7	1445.4	1355.4	1258.0	1178.5	1120.9	1069.7	1020.5	984.9
22.5°	1631.7	1528.1	1490.4	1432.8	1321.9	1236.1	1161.8	1091.6	1032.0	985.9	949.3
25°	1624.4	1518.7	1466.3	1420.3	1328.2	1223.5	1128.3	1059.2	1000.6	947.2	904.3
27.5°	1621.2	1491.4	1442.3	1396.2	1292.6	1186.9	1108.4	1029.9	962.9	915.8	871.8
30°	1617.0	1462.1	1402.5	1349.1	1253.9	1158.6	1064.4	996.4	932.5	872.9	828.9
32.5°	1589.8	1422.4	1361.7	1305.1	1202.6	1107.3	1033.0	960.8	891.7	836.3	796.5
35°	1581.5	1385.7	1306.2	1245.5	1145.0	1060.2	981.7	922.1	857.2	801.7	754.6
37.5°	1557.4	1348.1	1262.2	1184.8	1080.1	999.5	942.0	882.3	819.5	759.9	722.2
40°	1515.5	1304.1	1206.8	1127.2	1019.4	937.8	884.4	840.4	778.7	725.3	679.3
42.5°	1453.8	1259.1	1154.4	1070.7	951.4	875.0	831.0	789.2	736.8	681.4	643.7
45°	1382.6	1199.4	1102.1	1009.0	887.5	813.2	767.2	742.1	693.9	646.8	602.9
47.5°	1285.3	1137.7	1041.4	945.1	821.6	749.4	712.8	687.6	654.1	602.9	567.3
50°	1162.8	1058.1	967.1	881.3	756.7	687.6	651.0	632.2	603.9	567.3	532.7
52.5°	1026.7	966.0	890.7	811.1	690.8	625.9	592.4	577.7	556.8	522.3	493.0
55°	889.6	863.5	812.2	733.7	621.7	568.3	539.0	520.2	504.5	479.4	454.2
57.5°	767.2	754.6	719.0	658.3	564.1	508.7	483.5	471.0	458.4	439.6	414.5
60°	640.5	654.1	617.5	587.2	501.3	453.2	431.2	417.6	411.3	394.6	378.9
62.5°	530.6	543.2	522.3	499.2	438.5	395.6	382.0	369.5	365.3	350.6	334.9
65°	431.2	446.9	431.2	418.7	382.0	346.4	329.7	323.4	319.2	309.8	297.2
67.5°	343.3	359.0	351.7	336.0	324.5	295.1	285.7	279.4	277.4	270.0	259.6
70°	258.5	280.5	282.6	273.2	262.7	249.1	242.8	240.7	235.5	229.2	222.9
72.5°	186.3	211.4	212.5	212.5	206.2	206.2	199.9	196.8	196.8	190.5	183.2
75°	137.1	153.9	155.9	158.0	161.2	164.3	160.1	160.1	159.1	152.8	149.7
77.5°	91.1	105.7	110.9	118.3	122.5	122.5	124.5	126.6	124.5	121.4	119.3
80°	58.6	69.1	75.4	79.5	85.8	89.0	92.1	93.1	91.1	90.0	86.9
82.5°	38.7	41.9	45.0	50.2	57.6	62.8	62.8	61.8	63.8	62.8	61.8
85°	22.0	24.1	25.1	26.2	30.4	35.6	36.6	37.7	39.8	37.7	35.6
87.5°	8.4	9.4	9.4	9.4	11.5	12.6	15.7	19.9	18.8	16.7	16.7
90°	17.7	14.4	12.7	11.4	8.9	6.3	3.8	1.2	3.8	6.3	8.9
92.5°	23.1	20.8	19.6	20.4	21.9	23.5	25.0	26.6	25.0	23.5	21.9
95°	27.3	24.5	23.1	28.4	38.9	49.4	59.9	70.4	59.9	49.4	38.9
97.5°	76.2	89.3	95.8	99.4	106.6	113.7	120.9	128.1	120.9	113.7	106.6
100°	158.2	198.2	218.2	215.6	210.5	205.4	200.2	195.1	200.2	205.4	210.5
102.5°	219.3	264.0	286.3	284.6	281.3	278.0	274.6	271.3	274.6	278.0	281.3
105°	322.1	345.2	356.7	355.3	352.5	349.6	346.8	344.0	346.8	349.6	352.5
107.5°	437.5	433.6	431.7	430.6	428.3	426.0	423.7	421.4	423.7	426.0	428.3
110°	512.1	509.3	507.9	506.9	504.8	502.8	500.7	498.7	500.7	502.8	504.8

TEST NUMBER: P1010982

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	584.9	582.1	580.7	579.8	578.0	576.2	574.4	572.6	574.4	576.2	578.0
115°	655.7	653.4	652.2	651.4	649.9	648.4	646.8	645.3	646.8	648.4	649.9
117.5°	726.9	725.6	725.0	724.1	722.3	720.5	718.7	716.9	718.7	720.5	722.3
120°	794.2	793.5	793.1	791.9	789.6	787.3	785.0	782.7	785.0	787.3	789.6
122.5°	859.2	858.2	857.7	856.8	855.0	853.2	851.4	849.6	851.4	853.2	855.0
125°	920.4	919.4	918.9	917.9	915.8	913.8	911.7	909.7	911.7	913.8	915.8
127.5°	980.8	979.5	978.9	977.9	975.8	973.8	971.7	969.7	971.7	973.8	975.8
130°	1035.8	1034.8	1034.3	1033.3	1031.2	1029.2	1027.1	1025.1	1027.1	1029.2	1031.2
132.5°	1088.6	1087.8	1087.4	1086.4	1084.3	1082.3	1080.2	1078.2	1080.2	1082.3	1084.3
135°	1140.9	1139.9	1139.4	1138.6	1137.1	1135.6	1134.0	1132.5	1134.0	1135.6	1137.1
137.5°	1188.7	1188.2	1187.9	1186.9	1184.8	1182.7	1180.7	1178.6	1180.7	1182.7	1184.8
140°	1232.9	1232.1	1231.7	1230.9	1229.4	1227.9	1226.3	1224.8	1226.3	1227.9	1229.4
142.5°	1275.6	1274.8	1274.4	1273.6	1272.1	1270.6	1269.0	1267.5	1269.0	1270.6	1272.1
145°	1315.6	1315.1	1314.8	1313.9	1312.1	1310.4	1308.6	1306.8	1308.6	1310.4	1312.1
147.5°	1351.4	1350.9	1350.6	1350.0	1348.7	1347.4	1346.2	1344.9	1346.2	1347.4	1348.7
150°	1383.8	1383.3	1383.0	1382.6	1381.8	1381.1	1380.3	1379.5	1380.3	1381.1	1381.8
152.5°	1412.2	1411.9	1411.8	1411.7	1411.4	1411.2	1410.9	1410.7	1410.9	1411.2	1411.4
155°	1437.6	1437.3	1437.2	1437.5	1438.0	1438.5	1439.0	1439.5	1439.0	1438.5	1438.0
157.5°	1462.2	1462.5	1462.6	1462.6	1462.6	1462.6	1462.6	1462.6	1462.6	1462.6	1462.6
160°	1481.8	1482.1	1482.2	1482.3	1482.6	1482.9	1483.1	1483.4	1483.1	1482.9	1482.6
162.5°	1499.1	1499.4	1499.5	1499.9	1500.7	1501.4	1502.2	1503.0	1502.2	1501.4	1500.7
165°	1514.2	1514.5	1514.6	1515.0	1515.7	1516.5	1517.2	1518.0	1517.2	1516.5	1515.7
167.5°	1526.1	1526.1	1526.1	1526.6	1527.6	1528.7	1529.7	1530.7	1529.7	1528.7	1527.6
170°	1536.5	1536.5	1536.5	1537.0	1538.0	1539.1	1540.1	1541.1	1540.1	1539.1	1538.0
172.5°	1542.7	1542.4	1542.3	1542.9	1544.2	1545.5	1546.7	1548.0	1546.7	1545.5	1544.2
175°	1548.4	1548.1	1548.0	1548.6	1549.9	1551.2	1552.5	1553.8	1552.5	1551.2	1549.9
177.5°	1550.7	1550.4	1550.3	1550.9	1552.2	1553.5	1554.8	1556.1	1554.8	1553.5	1552.2
180°	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8

TEST NUMBER: P1010982

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5
2.5°	1206.8	1201.5	1199.4	1194.2	1181.6	1173.3	1163.9	1157.6	1158.6	1153.4	1156.5
5°	1169.1	1168.0	1160.7	1150.2	1132.5	1123.0	1106.3	1097.9	1093.7	1094.8	1088.5
7.5°	1137.7	1128.3	1123.0	1106.3	1089.5	1069.7	1056.0	1048.7	1042.4	1036.2	1032.0
10°	1102.1	1093.7	1085.4	1067.6	1044.5	1025.7	1006.9	999.5	990.1	985.9	982.8
12.5°	1064.4	1059.2	1048.7	1027.8	1001.6	983.8	961.9	957.7	945.1	936.7	934.6
15°	1029.9	1026.7	1007.9	983.8	957.7	939.9	921.0	908.5	887.5	891.7	884.4
17.5°	993.3	979.6	968.1	935.7	923.1	895.9	873.9	867.7	853.0	843.6	834.2
20°	952.4	944.1	929.4	908.5	878.1	846.7	830.0	819.5	811.1	796.5	792.3
22.5°	913.7	903.2	890.7	863.5	837.3	811.1	788.1	778.7	768.2	757.8	751.5
25°	883.4	867.7	854.0	820.6	794.4	772.4	757.8	742.1	727.4	721.1	719.0
27.5°	836.3	826.8	813.2	781.8	757.8	733.7	720.1	709.6	693.9	686.6	680.3
30°	805.9	787.1	771.4	746.2	722.2	696.0	683.4	670.9	661.5	652.0	644.7
32.5°	765.1	750.4	737.9	712.8	688.7	664.6	651.0	632.2	626.9	619.6	611.2
35°	725.3	715.9	702.3	675.1	648.9	632.2	617.5	599.7	593.4	588.2	580.9
37.5°	687.6	674.0	664.6	638.4	615.4	595.5	584.0	569.4	565.2	558.9	553.7
40°	655.2	641.6	632.2	606.0	581.9	561.0	553.7	539.0	532.7	525.4	522.3
42.5°	618.6	607.0	594.5	575.6	550.5	529.6	514.9	506.6	498.2	495.1	488.8
45°	579.8	569.4	559.9	539.0	512.8	498.2	485.6	474.1	467.8	462.6	458.4
47.5°	546.3	536.9	524.4	501.3	480.4	466.8	454.2	442.7	436.4	430.2	424.9
50°	507.6	502.4	488.8	466.8	446.9	431.2	419.7	409.2	405.0	397.7	389.3
52.5°	473.1	463.7	452.1	434.4	416.6	397.7	382.0	375.7	368.4	364.2	356.9
55°	432.3	426.0	413.4	397.7	378.9	363.2	351.7	343.3	333.9	329.7	320.3
57.5°	397.7	386.2	379.9	360.0	342.2	326.5	318.2	309.8	299.3	293.1	288.9
60°	360.0	349.6	340.2	323.4	310.8	294.1	281.5	274.2	266.9	258.5	254.3
62.5°	323.4	315.0	303.5	289.9	274.2	260.6	251.2	240.7	236.5	228.2	225.0
65°	283.6	277.4	267.9	252.2	239.7	228.2	218.7	210.4	206.2	203.0	201.0
67.5°	248.1	239.7	233.4	219.8	206.2	196.8	191.5	186.3	181.1	177.9	174.8
70°	211.4	205.1	198.9	186.3	176.9	168.5	164.3	160.1	157.0	153.9	150.7
72.5°	173.7	170.6	164.3	155.9	148.6	142.3	139.2	134.0	130.8	125.6	123.5
75°	143.4	138.2	135.0	127.7	121.4	116.2	112.0	105.7	101.5	99.4	98.4
77.5°	113.0	110.9	106.8	100.5	97.3	92.1	85.8	83.7	81.6	81.6	80.6
80°	84.8	81.6	78.5	73.3	70.1	65.9	65.9	65.9	64.9	65.9	64.9
82.5°	57.6	55.5	53.4	50.2	49.2	49.2	50.2	50.2	50.2	50.2	50.2
85°	33.5	33.5	33.5	34.5	33.5	33.5	34.5	35.6	34.5	34.5	33.5
87.5°	15.7	15.7	16.7	16.7	17.8	17.8	17.8	17.8	17.8	17.8	18.8
90°	11.4	12.7	14.4	17.7	21.0	24.4	27.7	28.7	29.7	30.8	31.8
92.5°	20.4	19.6	20.8	23.1	25.4	27.7	30.0	31.8	33.6	35.4	37.2
95°	28.4	23.1	24.5	27.3	30.2	33.0	35.8	37.6	39.4	41.2	43.0
97.5°	99.4	95.8	89.3	76.2	63.1	50.0	36.9	39.0	41.0	43.1	45.2
100°	215.6	218.2	198.2	158.2	118.1	78.1	38.1	40.1	42.2	44.2	46.3
102.5°	284.6	286.3	264.0	219.3	174.7	130.0	85.4	76.9	68.5	60.0	51.5
105°	355.3	356.7	345.2	322.1	299.0	275.9	252.8	207.4	162.0	116.6	71.2
107.5°	430.6	431.7	433.6	437.5	441.4	445.2	449.1	409.6	370.1	330.6	291.1
110°	506.9	507.9	509.3	512.1	515.0	517.8	520.6	512.1	503.7	495.2	486.7

TEST NUMBER: P1010982

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	579.8	580.7	582.1	584.9	587.8	590.6	593.4	595.7	598.0	600.3	602.6
115°	651.4	652.2	653.4	655.7	658.0	660.3	662.6	665.2	667.8	670.3	672.9
117.5°	724.1	725.0	725.6	726.9	728.2	729.4	730.7	732.8	734.8	736.9	739.0
120°	791.9	793.1	793.5	794.2	795.0	795.7	796.5	798.6	800.6	802.7	804.8
122.5°	856.8	857.7	858.2	859.2	860.3	861.3	862.3	863.6	864.9	866.2	867.5
125°	917.9	918.9	919.4	920.4	921.5	922.5	923.5	924.0	924.5	925.0	925.5
127.5°	977.9	978.9	979.5	980.8	982.1	983.4	984.7	985.5	986.3	987.0	987.8
130°	1033.3	1034.3	1034.8	1035.8	1036.9	1037.9	1038.9	1039.9	1041.0	1042.0	1043.1
132.5°	1086.4	1087.4	1087.8	1088.6	1089.3	1090.1	1090.9	1091.9	1092.9	1094.0	1095.0
135°	1138.6	1139.4	1139.9	1140.9	1142.0	1143.0	1144.0	1144.8	1145.6	1146.3	1147.1
137.5°	1186.9	1187.9	1188.2	1188.7	1189.2	1189.7	1190.2	1191.5	1192.7	1194.0	1195.3
140°	1230.9	1231.7	1232.1	1232.9	1233.6	1234.4	1235.2	1236.2	1237.2	1238.3	1239.3
142.5°	1273.6	1274.4	1274.8	1275.6	1276.3	1277.1	1277.9	1278.7	1279.5	1280.2	1281.0
145°	1313.9	1314.8	1315.1	1315.6	1316.1	1316.7	1317.2	1317.7	1318.2	1318.7	1319.2
147.5°	1350.0	1350.6	1350.9	1351.4	1351.9	1352.4	1352.9	1353.4	1353.9	1354.4	1354.9
150°	1382.6	1383.0	1383.3	1383.8	1384.3	1384.8	1385.3	1385.8	1386.3	1386.8	1387.3
152.5°	1411.7	1411.8	1411.9	1412.2	1412.5	1412.7	1413.0	1414.0	1415.0	1416.1	1417.1
155°	1437.5	1437.2	1437.3	1437.6	1437.9	1438.1	1438.4	1439.7	1440.9	1442.2	1443.5
157.5°	1462.6	1462.6	1462.5	1462.2	1462.0	1461.7	1461.5	1463.0	1464.6	1466.1	1467.6
160°	1482.3	1482.2	1482.1	1481.8	1481.6	1481.3	1481.1	1482.6	1484.2	1485.7	1487.2
162.5°	1499.9	1499.5	1499.4	1499.1	1498.9	1498.6	1498.4	1500.2	1502.0	1503.8	1505.6
165°	1515.0	1514.6	1514.5	1514.2	1513.9	1513.7	1513.4	1515.4	1517.5	1519.5	1521.6
167.5°	1526.6	1526.1	1526.1	1526.1	1526.1	1526.1	1526.1	1528.1	1530.2	1532.2	1534.3
170°	1537.0	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1538.5	1540.6	1542.6	1544.7
172.5°	1542.9	1542.3	1542.4	1542.7	1542.9	1543.2	1543.4	1545.4	1547.5	1549.5	1551.6
175°	1548.6	1548.0	1548.1	1548.4	1548.7	1548.9	1549.2	1551.0	1552.8	1554.6	1556.4
177.5°	1550.9	1550.3	1550.4	1550.7	1551.0	1551.2	1551.5	1553.5	1555.6	1557.6	1559.7
180°	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8

TEST NUMBER: P1010982

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5
2.5°	1155.5	1156.5	1153.4	1147.1	1146.1	1148.2	1154.4	1152.3	1147.1	1156.5	1148.2
5°	1091.6	1086.4	1084.3	1086.4	1080.1	1077.0	1083.3	1080.1	1083.3	1084.3	1087.4
7.5°	1029.9	1030.9	1024.6	1025.7	1017.3	1019.4	1019.4	1019.4	1022.6	1024.6	1028.8
10°	976.5	978.6	971.3	972.3	966.0	961.9	965.0	971.3	971.3	971.3	973.4
12.5°	933.6	924.2	918.9	917.9	910.6	908.5	914.8	916.8	922.1	922.1	925.2
15°	880.2	878.1	873.9	873.9	856.1	860.3	862.4	869.7	880.2	871.8	873.9
17.5°	832.1	826.8	821.6	819.5	817.4	811.1	819.5	818.5	824.7	825.8	828.9
20°	789.2	785.0	774.5	775.6	777.6	768.2	773.5	773.5	779.7	786.0	793.3
22.5°	747.3	743.1	737.9	740.0	733.7	731.6	731.6	736.8	744.2	749.4	748.3
25°	714.8	707.5	704.4	701.2	698.1	700.2	697.1	702.3	707.5	710.7	707.5
27.5°	678.2	675.1	668.8	665.7	660.4	662.5	664.6	668.8	671.9	671.9	675.1
30°	642.6	638.4	636.4	633.2	633.2	629.0	630.1	634.3	637.4	640.5	644.7
32.5°	608.1	605.0	601.8	601.8	599.7	598.7	597.6	603.9	603.9	610.2	610.2
35°	579.8	574.6	574.6	569.4	571.5	570.4	568.3	572.5	573.6	577.7	576.7
37.5°	548.4	548.4	546.3	541.1	536.9	538.0	543.2	543.2	546.3	545.3	548.4
40°	517.0	514.9	514.9	511.8	510.8	509.7	510.8	511.8	517.0	516.0	517.0
42.5°	485.6	486.7	481.4	481.4	481.4	478.3	479.4	480.4	482.5	484.6	487.7
45°	455.3	453.2	452.1	450.1	448.0	449.0	448.0	452.1	451.1	453.2	456.3
47.5°	422.8	419.7	418.7	414.5	414.5	416.6	415.5	418.7	419.7	422.8	420.7
50°	391.4	387.3	384.1	385.2	378.9	381.0	381.0	384.1	387.3	388.3	390.4
52.5°	354.8	353.8	352.7	347.5	346.4	345.4	346.4	347.5	351.7	354.8	355.9
55°	319.2	318.2	311.9	309.8	306.7	306.7	308.8	309.8	317.1	318.2	322.4
57.5°	286.8	283.6	276.3	275.3	275.3	275.3	272.1	276.3	278.4	283.6	283.6
60°	251.2	251.2	244.9	244.9	246.0	244.9	244.9	246.0	246.0	250.1	252.2
62.5°	222.9	221.9	221.9	219.8	218.7	219.8	218.7	218.7	219.8	222.9	226.1
65°	197.8	196.8	195.7	194.7	192.6	192.6	193.6	195.7	195.7	197.8	198.9
67.5°	173.7	173.7	171.6	171.6	170.6	169.6	170.6	169.6	173.7	173.7	174.8
70°	149.7	148.6	145.5	144.4	141.3	142.3	142.3	145.5	146.5	148.6	150.7
72.5°	120.4	120.4	118.3	116.2	117.2	115.1	115.1	116.2	116.2	119.3	120.4
75°	99.4	97.3	96.3	97.3	96.3	98.4	96.3	96.3	98.4	98.4	98.4
77.5°	81.6	81.6	80.6	80.6	81.6	80.6	81.6	81.6	81.6	80.6	81.6
80°	67.0	65.9	65.9	65.9	64.9	64.9	64.9	64.9	64.9	64.9	64.9
82.5°	50.2	50.2	49.2	50.2	50.2	49.2	50.2	49.2	49.2	50.2	50.2
85°	33.5	35.6	33.5	33.5	34.5	34.5	35.6	34.5	35.6	33.5	34.5
87.5°	17.8	18.8	18.8	17.8	17.8	18.8	18.8	18.8	19.9	17.8	18.8
90°	32.3	32.6	33.1	33.6	34.1	34.6	34.1	33.6	33.1	32.6	32.3
92.5°	38.1	38.2	38.5	38.7	39.0	39.2	39.0	38.7	38.5	38.2	38.1
95°	43.9	43.9	43.9	43.9	43.9	43.9	43.9	43.9	43.9	43.9	43.9
97.5°	46.2	46.3	46.6	46.8	47.1	47.3	47.1	46.8	46.6	46.3	46.2
100°	47.3	47.4	47.7	48.0	48.2	48.5	48.2	48.0	47.7	47.4	47.3
102.5°	47.3	47.6	48.1	48.6	49.1	49.6	49.1	48.6	48.1	47.6	47.3
105°	48.5	48.8	49.3	49.8	50.3	50.8	50.3	49.8	49.3	48.8	48.5
107.5°	271.3	254.5	220.9	187.3	153.7	120.1	153.7	187.3	220.9	254.5	271.3
110°	482.5	464.2	427.5	390.8	354.2	317.5	354.2	390.8	427.5	464.2	482.5

TEST NUMBER: P1010982

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	603.7	603.4	602.9	602.4	601.9	601.4	601.9	602.4	602.9	603.4	603.7
115°	674.2	674.7	675.7	676.8	677.8	678.8	677.8	676.8	675.7	674.7	674.2
117.5°	740.0	740.1	740.4	740.6	740.9	741.1	740.9	740.6	740.4	740.1	740.0
120°	805.8	805.8	805.8	805.8	805.8	805.8	805.8	805.8	805.8	805.8	805.8
122.5°	868.1	868.2	868.5	868.8	869.0	869.3	869.0	868.8	868.5	868.2	868.1
125°	925.8	926.1	926.6	927.1	927.6	928.1	927.6	927.1	926.6	926.1	925.8
127.5°	988.2	987.9	987.4	986.9	986.3	985.8	986.3	986.9	987.4	987.9	988.2
130°	1043.6	1043.3	1042.8	1042.3	1041.8	1041.3	1041.8	1042.3	1042.8	1043.3	1043.6
132.5°	1095.5	1095.1	1094.3	1093.6	1092.8	1092.0	1092.8	1093.6	1094.3	1095.1	1095.5
135°	1147.5	1147.1	1146.3	1145.6	1144.8	1144.0	1144.8	1145.6	1146.3	1147.1	1147.5
137.5°	1195.9	1195.6	1195.1	1194.6	1194.1	1193.6	1194.1	1194.6	1195.1	1195.6	1195.9
140°	1239.8	1239.5	1239.0	1238.5	1238.0	1237.5	1238.0	1238.5	1239.0	1239.5	1239.8
142.5°	1281.4	1281.0	1280.2	1279.5	1278.7	1277.9	1278.7	1279.5	1280.2	1281.0	1281.4
145°	1319.5	1319.5	1319.5	1319.5	1319.5	1319.5	1319.5	1319.5	1319.5	1319.5	1319.5
147.5°	1355.2	1354.6	1353.3	1352.0	1350.8	1349.5	1350.8	1352.0	1353.3	1354.6	1355.2
150°	1387.6	1387.2	1386.4	1385.7	1384.9	1384.1	1384.9	1385.7	1386.4	1387.2	1387.6
152.5°	1417.6	1417.0	1415.7	1414.4	1413.1	1411.8	1413.1	1414.4	1415.7	1417.0	1417.6
155°	1444.1	1443.3	1441.8	1440.3	1438.7	1437.2	1438.7	1440.3	1441.8	1443.3	1444.1
157.5°	1468.4	1467.4	1465.3	1463.2	1461.2	1459.1	1461.2	1463.2	1465.3	1467.4	1468.4
160°	1488.0	1487.1	1485.3	1483.5	1481.7	1479.9	1481.7	1483.5	1485.3	1487.1	1488.0
162.5°	1506.5	1505.7	1504.2	1502.6	1501.1	1499.5	1501.1	1502.6	1504.2	1505.7	1506.5
165°	1522.6	1521.7	1519.9	1518.2	1516.4	1514.6	1516.4	1518.2	1519.9	1521.7	1522.6
167.5°	1535.3	1534.3	1532.2	1530.2	1528.1	1526.1	1528.1	1530.2	1532.2	1534.3	1535.3
170°	1545.7	1544.7	1542.6	1540.6	1538.5	1536.5	1538.5	1540.6	1542.6	1544.7	1545.7
172.5°	1552.6	1551.5	1549.2	1546.9	1544.6	1542.3	1544.6	1546.9	1549.2	1551.5	1552.6
175°	1557.3	1556.3	1554.2	1552.1	1550.1	1548.0	1550.1	1552.1	1554.2	1556.3	1557.3
177.5°	1560.7	1559.4	1556.9	1554.3	1551.8	1549.2	1551.8	1554.3	1556.9	1559.4	1560.7
180°	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8

TEST NUMBER: P1010982

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5
2.5°	1156.5	1160.7	1156.5	1148.2	1156.5	1161.8	1167.0	1175.4	1179.6	1179.6	1185.8
5°	1090.6	1099.0	1095.8	1093.7	1102.1	1107.3	1115.7	1126.2	1137.7	1145.0	1153.4
7.5°	1032.0	1037.2	1042.4	1042.4	1050.8	1062.3	1074.9	1087.4	1102.1	1112.6	1118.8
10°	980.7	984.9	988.0	992.2	1004.8	1017.3	1034.1	1049.8	1062.3	1073.8	1084.3
12.5°	931.5	937.8	945.1	948.2	957.7	973.4	989.1	1007.9	1027.8	1039.3	1049.8
15°	884.4	887.5	895.9	905.3	913.7	930.5	950.3	970.2	987.0	1004.8	1014.2
17.5°	836.3	837.3	859.3	854.0	881.3	897.0	907.4	926.3	953.5	968.1	982.8
20°	789.2	799.6	809.0	814.3	828.9	846.7	877.1	891.7	913.7	927.3	939.9
22.5°	752.5	768.2	768.2	780.8	788.1	804.9	826.8	855.1	879.2	888.6	906.4
25°	720.1	727.4	740.0	744.2	757.8	772.4	787.1	817.4	843.6	856.1	868.7
27.5°	678.2	687.6	704.4	704.4	722.2	737.9	755.7	775.6	801.7	819.5	833.1
30°	645.8	655.2	662.5	674.0	681.4	696.0	727.4	742.1	765.1	780.8	797.5
32.5°	615.4	622.7	629.0	641.6	650.0	666.7	683.4	709.6	729.5	744.2	761.9
35°	581.9	589.3	597.6	607.0	619.6	635.3	651.0	673.0	692.9	706.5	721.1
37.5°	550.5	555.8	568.3	574.6	585.1	599.7	619.6	642.6	660.4	670.9	685.5
40°	520.2	524.4	533.8	545.3	552.6	564.1	585.1	605.0	626.9	639.5	651.0
42.5°	487.7	493.0	501.3	512.8	524.4	536.9	548.4	571.5	591.3	601.8	614.4
45°	459.5	462.6	468.9	480.4	491.9	501.3	519.1	540.1	558.9	567.3	580.9
47.5°	426.0	429.1	438.5	443.8	456.3	468.9	486.7	507.6	524.4	532.7	545.3
50°	391.4	394.6	400.9	412.4	420.7	434.4	450.1	467.8	488.8	500.3	507.6
52.5°	357.9	364.2	369.5	378.9	389.3	403.0	417.6	434.4	452.1	463.7	472.0
55°	324.5	329.7	336.0	341.2	353.8	366.3	383.1	398.8	414.5	424.9	434.4
57.5°	286.8	294.1	300.4	310.8	320.3	330.7	349.6	362.1	381.0	388.3	396.7
60°	254.3	261.7	266.9	275.3	283.6	297.2	309.8	325.5	341.2	350.6	361.1
62.5°	227.1	230.3	233.4	241.8	250.1	262.7	275.3	291.0	307.7	312.9	321.3
65°	199.9	203.0	208.3	215.6	221.9	229.2	242.8	255.4	271.1	279.4	282.6
67.5°	176.9	180.0	181.1	186.3	191.5	199.9	207.2	219.8	234.4	239.7	246.0
70°	150.7	155.9	157.0	161.2	163.3	168.5	176.9	186.3	197.8	207.2	212.5
72.5°	120.4	127.7	129.8	136.1	139.2	144.4	150.7	158.0	165.4	169.6	173.7
75°	98.4	100.5	101.5	106.8	112.0	119.3	122.5	126.6	132.9	138.2	142.3
77.5°	81.6	82.7	83.7	83.7	84.8	89.0	95.2	100.5	104.7	106.8	109.9
80°	65.9	64.9	64.9	65.9	65.9	65.9	68.0	75.4	77.5	82.7	81.6
82.5°	51.3	49.2	50.2	49.2	49.2	49.2	49.2	50.2	50.2	53.4	55.5
85°	33.5	34.5	33.5	33.5	32.4	33.5	32.4	32.4	31.4	31.4	30.4
87.5°	17.8	18.8	17.8	17.8	16.7	17.8	16.7	16.7	15.7	15.7	13.6
90°	31.8	30.8	29.7	28.7	27.7	24.4	21.0	17.7	14.4	12.7	11.4
92.5°	37.2	35.4	33.6	31.8	30.0	27.7	25.4	23.1	20.8	19.6	20.4
95°	43.0	41.2	39.4	37.6	35.8	33.0	30.2	27.3	24.5	23.1	28.4
97.5°	45.2	43.1	41.0	39.0	36.9	50.0	63.1	76.2	89.3	95.8	99.4
100°	46.3	44.2	42.2	40.1	38.1	78.1	118.1	158.2	198.2	218.2	215.6
102.5°	51.5	60.0	68.5	76.9	85.4	130.0	174.7	219.3	264.0	286.3	284.6
105°	71.2	116.6	162.0	207.4	252.8	275.9	299.0	322.1	345.2	356.7	355.3
107.5°	291.1	330.6	370.1	409.6	449.1	445.2	441.4	437.5	433.6	431.7	430.6
110°	486.7	495.2	503.7	512.1	520.6	517.8	515.0	512.1	509.3	507.9	506.9

TEST NUMBER: P1010982

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	602.6	600.3	598.0	595.7	593.4	590.6	587.8	584.9	582.1	580.7	579.8
115°	672.9	670.3	667.8	665.2	662.6	660.3	658.0	655.7	653.4	652.2	651.4
117.5°	739.0	736.9	734.8	732.8	730.7	729.4	728.2	726.9	725.6	725.0	724.1
120°	804.8	802.7	800.6	798.6	796.5	795.7	795.0	794.2	793.5	793.1	791.9
122.5°	867.5	866.2	864.9	863.6	862.3	861.3	860.3	859.2	858.2	857.7	856.8
125°	925.5	925.0	924.5	924.0	923.5	922.5	921.5	920.4	919.4	918.9	917.9
127.5°	987.8	987.0	986.3	985.5	984.7	983.4	982.1	980.8	979.5	978.9	977.9
130°	1043.1	1042.0	1041.0	1039.9	1038.9	1037.9	1036.9	1035.8	1034.8	1034.3	1033.3
132.5°	1095.0	1094.0	1092.9	1091.9	1090.9	1090.1	1089.3	1088.6	1087.8	1087.4	1086.4
135°	1147.1	1146.3	1145.6	1144.8	1144.0	1143.0	1142.0	1140.9	1139.9	1139.4	1138.6
137.5°	1195.3	1194.0	1192.7	1191.5	1190.2	1189.7	1189.2	1188.7	1188.2	1187.9	1186.9
140°	1239.3	1238.3	1237.2	1236.2	1235.2	1234.4	1233.6	1232.9	1232.1	1231.7	1230.9
142.5°	1281.0	1280.2	1279.5	1278.7	1277.9	1277.1	1276.3	1275.6	1274.8	1274.4	1273.6
145°	1319.2	1318.7	1318.2	1317.7	1317.2	1316.7	1316.1	1315.6	1315.1	1314.8	1313.9
147.5°	1354.9	1354.4	1353.9	1353.4	1352.9	1352.4	1351.9	1351.4	1350.9	1350.6	1350.0
150°	1387.3	1386.8	1386.3	1385.8	1385.3	1384.8	1384.3	1383.8	1383.3	1383.0	1382.6
152.5°	1417.1	1416.1	1415.0	1414.0	1413.0	1412.7	1412.5	1412.2	1411.9	1411.8	1411.7
155°	1443.5	1442.2	1440.9	1439.7	1438.4	1438.1	1437.9	1437.6	1437.3	1437.2	1437.5
157.5°	1467.6	1466.1	1464.6	1463.0	1461.5	1461.7	1462.0	1462.2	1462.5	1462.6	1462.6
160°	1487.2	1485.7	1484.2	1482.6	1481.1	1481.3	1481.6	1481.8	1482.1	1482.2	1482.3
162.5°	1505.6	1503.8	1502.0	1500.2	1498.4	1498.6	1498.9	1499.1	1499.4	1499.5	1499.9
165°	1521.6	1519.5	1517.5	1515.4	1513.4	1513.7	1513.9	1514.2	1514.5	1514.6	1515.0
167.5°	1534.3	1532.2	1530.2	1528.1	1526.1	1526.1	1526.1	1526.1	1526.1	1526.1	1526.6
170°	1544.7	1542.6	1540.6	1538.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1537.0
172.5°	1551.6	1549.5	1547.5	1545.4	1543.4	1543.2	1542.9	1542.7	1542.4	1542.3	1542.9
175°	1556.4	1554.6	1552.8	1551.0	1549.2	1548.9	1548.7	1548.4	1548.1	1548.0	1548.6
177.5°	1559.7	1557.6	1555.6	1553.5	1551.5	1551.2	1551.0	1550.7	1550.4	1550.3	1550.9
180°	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8

TEST NUMBER: P1010982

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1222.5	1222.5	1222.5	1222.5
2.5°	1191.1	1198.4	1213.0	1225.6
5°	1165.9	1177.5	1199.4	1221.4
7.5°	1135.6	1153.4	1181.6	1212.0
10°	1106.3	1129.3	1163.9	1199.4
12.5°	1077.0	1101.1	1137.7	1183.7
15°	1042.4	1067.6	1111.5	1167.0
17.5°	1012.1	1045.6	1085.4	1140.8
20°	979.6	1004.8	1056.0	1114.7
22.5°	938.8	980.7	1028.8	1090.6
25°	906.4	943.0	991.2	1061.3
27.5°	866.6	909.5	968.1	1029.9
30°	834.2	869.7	924.2	998.5
32.5°	796.5	838.3	894.9	968.1
35°	763.0	798.6	852.0	926.3
37.5°	723.2	761.9	821.6	887.5
40°	688.7	726.4	782.9	844.6
42.5°	646.8	686.6	743.1	795.4
45°	613.3	650.0	695.0	743.1
47.5°	572.5	611.2	655.2	688.7
50°	535.9	571.5	606.0	634.3
52.5°	496.1	528.5	559.9	580.9
55°	459.5	484.6	509.7	524.4
57.5°	416.6	440.6	461.6	469.9
60°	378.9	398.8	412.4	421.8
62.5°	339.1	353.8	364.2	369.5
65°	300.4	310.8	316.1	321.3
67.5°	260.6	270.0	273.2	279.4
70°	218.7	229.2	231.3	234.4
72.5°	187.3	187.3	191.5	195.7
75°	149.7	151.8	153.9	153.9
77.5°	117.2	117.2	119.3	120.4
80°	85.8	86.9	86.9	85.8
82.5°	58.6	60.7	58.6	57.6
85°	32.4	36.6	34.5	34.5
87.5°	13.6	13.6	15.7	13.6
90°	8.9	6.3	3.8	1.2
92.5°	21.9	23.5	25.0	26.6
95°	38.9	49.4	59.9	70.4
97.5°	106.6	113.7	120.9	128.1
100°	210.5	205.4	200.2	195.1
102.5°	281.3	278.0	274.6	271.3
105°	352.5	349.6	346.8	344.0
107.5°	428.3	426.0	423.7	421.4
110°	504.8	502.8	500.7	498.7

TEST NUMBER: P1010982

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	578.0	576.2	574.4	572.6
115°	649.9	648.4	646.8	645.3
117.5°	722.3	720.5	718.7	716.9
120°	789.6	787.3	785.0	782.7
122.5°	855.0	853.2	851.4	849.6
125°	915.8	913.8	911.7	909.7
127.5°	975.8	973.8	971.7	969.7
130°	1031.2	1029.2	1027.1	1025.1
132.5°	1084.3	1082.3	1080.2	1078.2
135°	1137.1	1135.6	1134.0	1132.5
137.5°	1184.8	1182.7	1180.7	1178.6
140°	1229.4	1227.9	1226.3	1224.8
142.5°	1272.1	1270.6	1269.0	1267.5
145°	1312.1	1310.4	1308.6	1306.8
147.5°	1348.7	1347.4	1346.2	1344.9
150°	1381.8	1381.1	1380.3	1379.5
152.5°	1411.4	1411.2	1410.9	1410.7
155°	1438.0	1438.5	1439.0	1439.5
157.5°	1462.6	1462.6	1462.6	1462.6
160°	1482.6	1482.9	1483.1	1483.4
162.5°	1500.7	1501.4	1502.2	1503.0
165°	1515.7	1516.5	1517.2	1518.0
167.5°	1527.6	1528.7	1529.7	1530.7
170°	1538.0	1539.1	1540.1	1541.1
172.5°	1544.2	1545.5	1546.7	1548.0
175°	1549.9	1551.2	1552.5	1553.8
177.5°	1552.2	1553.5	1554.8	1556.1
180°	1553.8	1553.8	1553.8	1553.8

(END OF REPORT)