

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011039

Luminaire Tested: S123DIP-B1000D1025UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011039
REPORT IS A COMBINATION OF REPORTS P989054 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D1025UB35-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7923.0 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011039

CATALOG NUMBER: S123DIP-B1000D1025UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1011039

CATALOG NUMBER: S123DIP-B1000D1025UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	87	91	88	85	82	75	73	71	64	62	60	53	52	51
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	37	34	32
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	34	31	28
6	64	52	44	38	59	49	41	36	42	37	32	36	32	29	31	27	25
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20
9	51	39	32	26	47	37	30	25	32	27	23	28	23	20	24	20	18
10	48	36	29	24	44	34	27	23	30	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15093	15093	15093	15093
5°	15103	17390	15147	12979
10°	15007	21044	15022	11334
15°	14800	24957	14919	10202
20°	14621	28734	14652	9388
25°	14355	29457	14387	8963
30°	14167	24337	14167	8685
35°	13932	16277	13844	8438
40°	13651	11750	13482	8062
45°	13298	9307	12915	7594
50°	12438	7904	11998	7134
55°	11497	6945	11029	6620
60°	10542	6047	9981	6083
65°	9493	5178	9031	5365
70°	8402	4299	7842	4522
75°	7186	3242	6718	3490
80°	5679	2164	5239	2293
85°	3919	993	3131	904

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 24341 cd/sqm

TEST NUMBER: P1011039

CATALOG NUMBER: S123DIP-B1000D1025UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.9	1.7
10°-20°	442.9	5.6
20°-30°	745.3	9.4
30°-40°	842.2	10.6
40°-50°	754.3	9.5
50°-60°	608.9	7.7
60°-70°	424.3	5.4
70°-80°	222.7	2.8
80°-90°	56.1	0.7
90°-100°	266.1	3.4
100°-110°	779.0	9.8
110°-120°	760.7	9.6
120°-130°	605.8	7.6
130°-140°	478.0	6.0
140°-150°	356.6	4.5
150°-160°	248.6	3.1
160°-170°	146.0	1.8
170°-180°	47.5	0.6
0°-30°	1326.1	16.7
0°-40°	2168.3	27.4
0°-60°	3531.6	44.6
0°-90°	4234.7	53.4
90°-120°	1805.8	22.8
90°-150°	3246.1	41.0
90°-180°	3688.0	46.5
0°-180°	7923.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1402	1402	1402	1402	1402	
5°	1401	1666	1405	1243	1401	133
15°	1337	2480	1348	1014	1337	378
25°	1223	2943	1226	895	1223	564
35°	1079	1586	1072	822	1079	675
45°	895	856	870	698	895	685
55°	634	582	609	554	634	568
65°	393	378	374	391	393	391
75°	189	194	177	209	189	203
85°	41	45	33	41	41	47
90°	2	29	2	29	2	5
95°	34	115	34	115	34	36
105°	115	1262	115	1262	115	122
115°	204	1536	204	1536	204	201
125°	283	1211	283	1211	283	251
135°	332	982	332	982	332	256
145°	378	767	378	767	378	237
155°	430	636	430	636	430	198
165°	470	555	470	555	470	132
175°	489	499	489	499	489	46
180°	490	490	490	490	490	

TEST NUMBER: P1011039

CATALOG NUMBER: S123DIP-B1000D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2
2.5°	1406.3	1417.1	1422.6	1430.7	1438.9	1451.1	1455.2	1462.0	1459.2	1464.7	1467.4
5°	1400.8	1419.8	1436.1	1456.5	1475.5	1489.1	1502.7	1524.5	1540.8	1543.5	1555.7
7.5°	1391.3	1418.5	1447.0	1475.5	1512.2	1534.0	1558.4	1588.3	1612.8	1652.2	1667.1
10°	1379.1	1417.1	1457.9	1497.3	1547.6	1581.5	1611.4	1661.7	1712.0	1752.7	1790.8
12.5°	1360.1	1407.6	1460.6	1519.0	1584.2	1623.6	1664.4	1731.0	1807.1	1869.6	1910.3
15°	1337.0	1396.7	1464.7	1527.2	1599.2	1672.6	1716.0	1790.8	1899.5	1957.9	2062.5
17.5°	1317.9	1379.1	1447.0	1544.8	1642.7	1716.0	1747.3	1884.5	1959.2	2057.1	2175.3
20°	1288.0	1365.5	1452.5	1550.3	1676.6	1721.5	1785.3	1923.9	2016.3	2144.0	2289.4
22.5°	1256.8	1339.7	1444.3	1546.2	1687.5	1735.1	1822.0	1932.1	2078.8	2205.2	2365.5
25°	1222.8	1312.5	1418.5	1539.4	1678.0	1747.3	1828.8	1964.7	2123.6	2282.6	2430.7
27.5°	1188.9	1286.7	1396.7	1517.7	1652.2	1733.7	1815.2	1956.5	2160.3	2332.9	2521.7
30°	1156.3	1254.1	1364.1	1487.8	1629.1	1707.9	1785.3	1962.0	2188.9	2383.2	2573.4
32.5°	1120.9	1221.5	1337.0	1440.2	1582.9	1667.1	1754.1	1962.0	2206.5	2413.1	2587.0
35°	1078.8	1182.1	1281.3	1384.5	1525.8	1619.6	1717.4	1948.4	2222.8	2422.6	2529.9
37.5°	1038.0	1129.1	1214.7	1315.2	1463.3	1563.9	1676.6	1932.1	2214.7	2381.8	2411.7
40°	991.9	1082.9	1152.2	1245.9	1402.2	1519.0	1633.2	1910.3	2179.4	2285.3	2198.4
42.5°	947.0	1019.0	1078.8	1169.8	1339.7	1453.8	1577.5	1870.9	2110.1	2131.8	1936.1
45°	895.4	947.0	1000.0	1103.3	1271.7	1388.6	1525.8	1813.9	1998.6	1936.1	1688.9
47.5°	828.8	875.0	933.4	1028.5	1199.7	1320.7	1451.1	1740.5	1837.0	1706.5	1436.1
50°	764.9	804.4	858.7	951.1	1123.6	1241.9	1380.4	1625.0	1672.6	1467.4	1237.8
52.5°	701.1	731.0	784.0	876.4	1048.9	1163.0	1289.4	1506.8	1479.6	1259.5	1055.7
55°	634.5	660.3	710.6	801.6	962.0	1070.7	1191.6	1361.4	1290.8	1081.5	918.5
57.5°	569.3	596.5	648.1	724.2	875.0	981.0	1077.4	1210.6	1104.6	937.5	793.5
60°	510.9	534.0	573.4	648.1	785.3	870.9	959.2	1050.3	962.0	800.3	690.2
62.5°	449.7	471.5	508.2	576.1	694.3	770.4	841.0	915.8	817.9	699.7	601.9
65°	392.7	410.3	444.3	506.8	603.3	665.8	722.8	774.5	695.7	587.0	513.6
67.5°	341.0	356.0	384.5	440.2	521.7	566.6	612.8	656.3	589.7	502.7	440.2
70°	285.3	297.6	323.4	364.1	429.3	475.5	509.5	542.1	482.3	413.0	370.9
72.5°	236.4	248.6	264.9	307.1	351.9	380.4	417.1	434.8	400.8	343.8	301.6
75°	188.9	198.4	213.3	240.5	282.6	301.6	324.7	338.3	307.1	269.0	243.2
77.5°	148.1	152.2	163.0	182.1	210.6	232.3	250.0	258.2	236.4	212.0	190.2
80°	104.6	110.1	118.2	134.5	156.3	163.0	173.9	183.4	169.8	148.1	134.5
82.5°	69.3	76.1	80.2	87.0	100.5	108.7	111.4	119.6	107.3	99.2	93.8
85°	40.8	43.5	44.8	48.9	55.7	59.8	63.9	65.2	62.5	61.1	55.7
87.5°	20.4	20.4	20.4	23.1	24.5	27.2	28.5	28.5	28.5	27.2	25.8
90°	2.0	4.0	6.0	8.9	10.9	11.9	12.9	15.9	18.9	21.8	24.8
92.5°	14.9	21.8	31.8	40.7	50.6	59.6	68.5	100.2	152.9	204.5	184.6
95°	33.7	36.7	47.6	64.5	90.3	109.6	129.0	213.4	361.3	524.1	588.6
97.5°	53.6	54.6	63.5	78.4	104.2	125.6	146.9	230.3	402.0	675.9	905.2
100°	73.4	74.4	81.4	95.3	119.1	138.4	157.8	227.3	374.2	635.2	940.0
102.5°	94.3	96.3	102.2	115.1	136.0	153.4	170.7	231.3	350.4	575.7	875.4
105°	115.1	118.1	124.1	136.0	154.8	170.2	185.6	239.2	341.4	529.0	798.0
107.5°	137.0	140.0	145.9	157.8	175.7	190.1	204.5	252.1	339.5	495.3	729.5
110°	160.8	163.8	168.7	179.7	196.5	210.4	224.3	269.0	344.4	477.4	673.0

TEST NUMBER: P1011039

CATALOG NUMBER: S123DIP-B1000D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	182.6	185.6	190.6	201.5	218.4	231.8	245.2	285.9	354.3	467.5	635.2
115°	203.5	207.4	213.4	223.3	240.2	253.6	267.0	304.7	365.3	466.5	610.4
117.5°	224.3	229.3	234.2	243.2	262.0	274.4	286.9	324.6	379.2	467.5	593.6
120°	246.2	249.1	254.1	264.0	282.9	295.3	307.7	343.4	395.0	471.5	582.6
122.5°	265.0	268.0	273.0	283.9	301.7	315.1	328.5	363.3	409.9	478.4	575.7
125°	282.9	284.9	290.8	301.7	320.6	334.0	347.4	382.1	425.8	485.4	569.7
127.5°	296.8	299.8	306.7	317.6	338.5	351.9	365.3	399.0	438.7	493.3	566.8
130°	309.7	312.7	321.6	333.5	354.3	367.7	381.1	413.9	451.6	501.2	563.8
132.5°	319.6	323.6	333.5	348.4	369.2	382.1	395.0	426.8	463.5	507.2	562.8
135°	331.5	335.5	346.4	361.3	382.1	395.5	408.9	439.7	473.5	513.2	561.8
137.5°	342.4	346.4	357.3	373.2	394.0	406.4	418.9	448.6	481.4	517.1	559.8
140°	353.4	358.3	368.2	384.1	404.0	416.4	428.8	457.6	487.3	521.1	558.8
142.5°	365.3	369.2	380.2	394.0	413.9	425.3	436.7	464.5	493.3	524.1	556.8
145°	378.2	381.1	390.1	405.0	421.8	433.2	444.7	470.5	497.3	525.1	554.8
147.5°	391.1	393.1	402.0	414.9	431.8	441.7	451.6	475.4	500.3	525.1	551.9
150°	404.0	405.0	412.9	425.8	439.7	448.6	457.6	480.4	501.2	525.1	547.9
152.5°	416.9	416.9	424.8	435.7	447.6	456.0	464.5	483.4	503.2	522.1	542.9
155°	429.8	429.8	435.7	445.7	456.6	463.6	470.5	487.3	503.2	520.1	537.0
157.5°	439.7	440.7	445.7	454.6	464.5	470.0	475.4	489.3	504.2	517.1	532.0
160°	451.6	451.6	455.6	463.5	470.5	475.4	480.4	492.3	504.2	515.1	526.1
162.5°	460.5	460.5	463.5	469.5	475.4	479.4	483.4	493.3	503.2	511.2	520.1
165°	469.5	468.5	470.5	475.4	479.4	482.9	486.4	494.3	501.2	507.2	514.1
167.5°	476.4	475.4	476.4	480.4	483.4	485.8	488.3	494.3	500.3	503.2	508.2
170°	482.4	480.4	481.4	484.4	486.4	487.4	488.3	493.3	497.3	499.3	502.2
172.5°	486.4	485.4	485.4	487.3	488.3	488.8	489.3	493.3	496.3	496.3	497.3
175°	489.3	488.3	487.3	489.3	489.3	489.8	490.3	492.3	494.3	493.3	493.3
177.5°	491.3	490.3	489.3	490.3	490.3	490.3	490.3	491.3	493.3	491.3	490.3
180°	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3

TEST NUMBER: P1011039

CATALOG NUMBER: S123DIP-B1000D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2
2.5°	1476.9	1479.6	1489.1	1495.9	1509.5	1508.2	1508.2	1506.8	1502.7	1509.5	1513.6
5°	1580.2	1603.3	1606.0	1635.9	1637.2	1649.5	1657.6	1650.8	1667.1	1665.8	1653.5
7.5°	1707.9	1739.1	1754.1	1782.6	1815.2	1807.1	1838.3	1843.8	1841.0	1854.6	1864.1
10°	1847.8	1902.2	1940.2	1993.2	2006.8	2015.0	2035.3	2053.0	2088.3	2061.1	2078.8
12.5°	2008.2	2047.6	2097.8	2182.1	2224.2	2251.4	2260.9	2273.1	2297.6	2282.6	2284.0
15°	2142.7	2195.7	2281.3	2385.9	2398.1	2432.1	2423.9	2497.3	2532.6	2479.6	2509.5
17.5°	2282.6	2353.3	2455.2	2546.2	2597.8	2620.9	2642.7	2713.3	2710.6	2702.5	2709.2
20°	2372.3	2487.8	2614.1	2735.1	2750.0	2767.7	2826.1	2856.0	2850.6	2873.7	2888.6
22.5°	2498.6	2620.9	2755.4	2835.6	2869.6	2890.0	2936.2	2955.2	2963.3	2968.8	2959.2
25°	2604.6	2735.1	2834.2	2904.9	2925.3	2936.2	2951.1	2956.5	2952.5	2942.9	2951.1
27.5°	2676.6	2781.3	2849.2	2881.8	2870.9	2853.3	2824.7	2805.7	2763.6	2743.2	2767.7
30°	2706.5	2752.7	2773.1	2718.8	2664.4	2620.9	2566.6	2466.0	2387.2	2410.3	2379.1
32.5°	2659.0	2629.1	2531.3	2391.3	2349.2	2278.5	2125.0	2006.8	2010.9	1948.4	1974.2
35°	2519.0	2383.2	2198.4	1986.4	1930.7	1892.7	1724.2	1698.4	1644.0	1585.6	1601.9
37.5°	2271.7	2073.4	1849.2	1692.9	1610.1	1527.2	1432.1	1375.0	1342.4	1317.9	1337.0
40°	1970.1	1728.3	1543.5	1403.5	1332.9	1279.9	1214.7	1157.6	1120.9	1116.9	1123.6
42.5°	1673.9	1470.1	1300.3	1167.1	1144.0	1081.5	1039.4	994.6	983.7	966.0	975.5
45°	1417.1	1251.4	1111.4	1002.7	975.5	959.2	907.6	879.1	866.9	856.0	872.3
47.5°	1231.0	1057.1	955.2	889.9	862.8	835.6	807.1	788.0	778.5	779.9	778.5
50°	1051.6	923.9	834.2	784.0	767.7	748.6	725.5	713.3	709.2	697.0	706.5
52.5°	904.9	812.5	750.0	702.4	690.2	676.6	657.6	650.8	641.3	638.6	638.6
55°	786.7	714.7	664.4	633.2	618.2	607.3	596.5	588.3	581.5	581.5	581.5
57.5°	694.3	631.8	595.1	567.9	562.5	551.6	539.4	539.4	529.9	528.5	532.6
60°	615.5	559.8	531.3	508.2	500.0	497.3	485.1	485.1	482.3	475.5	481.0
62.5°	535.3	494.6	470.1	452.4	444.3	444.3	434.8	428.0	428.0	429.3	426.6
65°	462.0	432.1	410.3	396.7	392.7	387.2	385.9	380.4	376.4	377.7	376.4
67.5°	396.7	373.6	358.7	347.8	341.0	338.3	334.2	334.2	331.5	332.9	326.1
70°	338.3	315.2	303.0	292.1	289.4	289.4	284.0	285.3	282.6	286.7	284.0
72.5°	278.5	260.9	251.4	247.3	244.6	243.2	240.5	237.8	236.4	239.1	237.8
75°	225.5	210.6	203.8	201.1	198.4	198.4	197.0	195.7	194.3	194.3	194.3
77.5°	175.3	165.8	157.6	160.3	156.3	157.6	153.5	153.5	154.9	153.5	153.5
80°	129.1	122.3	122.3	119.6	114.1	116.8	116.8	112.8	111.4	114.1	110.1
82.5°	85.6	84.2	81.5	80.2	77.4	78.8	77.4	76.1	74.7	77.4	74.7
85°	50.3	50.3	48.9	46.2	48.9	47.6	46.2	46.2	44.8	44.8	44.8
87.5°	25.8	23.1	23.1	21.7	23.1	20.4	21.7	20.4	19.0	20.4	19.0
90°	23.8	24.8	25.8	26.8	27.8	28.8	27.8	28.8	29.8	28.8	29.8
92.5°	138.0	98.3	76.4	66.5	63.0	59.6	57.6	53.6	54.6	52.6	54.6
95°	477.4	357.3	242.2	189.6	171.7	153.8	135.0	126.1	119.1	115.1	119.1
97.5°	936.0	820.9	619.4	488.3	431.8	375.2	308.7	271.0	247.1	236.2	247.1
100°	1135.5	1170.2	1089.8	973.7	903.2	832.8	732.5	660.1	621.3	622.3	621.3
102.5°	1145.4	1286.4	1303.2	1247.7	1209.4	1171.2	1098.8	1045.2	1014.4	985.6	1014.4
105°	1082.9	1290.3	1389.6	1408.4	1395.5	1382.6	1337.0	1299.3	1267.5	1262.5	1267.5
107.5°	993.6	1230.8	1386.6	1464.0	1477.4	1490.8	1484.9	1467.0	1454.1	1443.2	1454.1
110°	910.2	1137.5	1320.1	1445.2	1480.0	1514.7	1542.4	1550.4	1548.4	1546.4	1548.4

TEST NUMBER: P1011039

CATALOG NUMBER: S123DIP-B1000D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	837.7	1045.2	1232.8	1376.7	1423.8	1471.0	1527.6	1556.3	1566.3	1567.3	1566.3
115°	782.1	965.8	1138.5	1284.4	1338.5	1392.6	1467.0	1510.7	1530.5	1535.5	1530.5
117.5°	745.4	904.2	1057.1	1191.1	1247.2	1303.2	1380.7	1429.3	1459.1	1466.0	1459.1
120°	717.6	857.6	991.6	1110.7	1160.8	1210.9	1289.3	1344.9	1368.7	1374.7	1368.7
122.5°	694.8	820.9	939.0	1047.2	1092.8	1138.5	1206.0	1254.6	1281.4	1289.3	1281.4
125°	675.9	789.1	897.3	992.6	1032.3	1072.0	1135.5	1179.2	1204.0	1210.9	1204.0
127.5°	658.1	760.3	858.6	945.9	982.6	1019.4	1076.9	1114.6	1137.5	1143.4	1137.5
130°	644.2	733.5	822.8	903.2	937.0	970.7	1023.3	1059.1	1079.9	1087.8	1079.9
132.5°	631.3	708.7	789.1	862.5	894.3	926.1	974.7	1010.4	1028.3	1033.3	1028.3
135°	620.4	686.9	757.3	821.8	850.1	878.4	927.1	956.8	974.7	981.6	974.7
137.5°	610.4	666.0	725.6	783.1	808.4	833.8	875.4	906.2	921.1	927.1	921.1
140°	601.5	648.1	698.8	746.4	767.8	789.1	826.8	854.6	870.5	869.5	870.5
142.5°	593.6	631.3	673.0	712.7	730.6	748.4	779.2	803.0	816.9	815.9	816.9
145°	586.6	618.4	651.1	682.9	697.3	711.7	736.5	757.3	765.3	767.3	765.3
147.5°	579.7	607.4	634.2	661.0	671.4	681.9	701.7	716.6	724.6	725.6	724.6
150°	572.7	595.5	618.4	639.2	648.7	658.1	673.0	683.9	689.8	689.8	689.8
152.5°	564.8	584.6	603.5	621.3	628.8	636.2	647.2	657.1	660.1	660.1	660.1
155°	556.8	573.7	589.6	604.5	610.4	616.4	625.3	633.3	635.2	636.2	635.2
157.5°	547.9	561.8	575.7	587.6	592.6	597.5	605.5	611.4	613.4	613.4	613.4
160°	539.0	551.9	562.8	572.7	576.2	579.7	586.6	592.6	592.6	591.6	592.6
162.5°	530.0	540.0	548.9	557.8	560.8	563.8	567.7	572.7	572.7	571.7	572.7
165°	522.1	530.0	536.0	542.9	545.4	547.9	551.9	555.8	554.8	554.8	554.8
167.5°	514.1	521.1	526.1	530.0	532.0	534.0	536.0	539.0	538.0	538.0	538.0
170°	507.2	512.2	515.1	519.1	520.1	521.1	522.1	524.1	523.1	523.1	523.1
172.5°	500.3	504.2	506.2	509.2	509.7	510.2	510.2	512.2	510.2	509.2	510.2
175°	495.3	497.3	498.3	500.3	500.3	500.3	500.3	501.2	500.3	499.3	500.3
177.5°	491.3	492.3	493.3	494.3	494.3	494.3	493.3	494.3	492.3	492.3	492.3
180°	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3

TEST NUMBER: P1011039

CATALOG NUMBER: S123DIP-B1000D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2
2.5°	1502.7	1506.8	1495.9	1493.2	1493.2	1498.6	1494.6	1457.9	1464.7	1456.5	1453.8
5°	1668.5	1660.3	1649.5	1644.0	1637.2	1618.2	1616.9	1574.7	1566.6	1539.4	1527.2
7.5°	1850.5	1843.8	1811.1	1807.1	1804.4	1786.7	1741.9	1697.0	1664.4	1633.2	1603.3
10°	2058.4	2038.1	2023.1	1993.2	1978.3	1953.8	1895.4	1853.3	1797.6	1750.0	1687.5
12.5°	2308.4	2285.3	2235.1	2213.3	2194.3	2126.4	2067.9	2020.4	1911.7	1879.1	1801.6
15°	2491.9	2442.9	2437.5	2390.0	2387.2	2312.5	2201.1	2149.5	2065.2	1945.7	1865.5
17.5°	2690.2	2646.7	2612.8	2555.7	2547.6	2476.9	2395.4	2269.0	2176.6	2062.5	1960.6
20°	2835.6	2812.5	2754.1	2731.0	2683.4	2623.6	2539.4	2383.2	2270.4	2156.3	2031.3
22.5°	2951.1	2928.0	2881.8	2850.6	2823.4	2745.9	2645.4	2512.2	2357.3	2207.9	2078.8
25°	2949.7	2942.9	2923.9	2909.0	2888.6	2831.5	2747.3	2619.6	2447.0	2282.6	2103.3
27.5°	2782.6	2801.6	2834.2	2850.6	2846.5	2838.3	2790.8	2683.4	2528.5	2332.9	2131.8
30°	2434.8	2504.1	2565.2	2646.7	2671.2	2731.0	2758.2	2697.0	2573.4	2391.3	2168.5
32.5°	2019.0	2119.6	2252.7	2297.6	2375.0	2490.5	2619.6	2642.7	2565.2	2425.3	2191.6
35°	1656.3	1739.1	1842.4	1913.0	1982.3	2169.8	2332.9	2474.2	2500.0	2407.6	2186.1
37.5°	1370.9	1429.4	1520.4	1580.2	1644.0	1804.4	2032.6	2216.0	2345.1	2347.8	2171.2
40°	1164.4	1190.2	1269.0	1312.5	1373.6	1512.2	1716.0	1955.2	2144.0	2231.0	2131.8
42.5°	986.4	1020.4	1085.6	1118.2	1157.6	1278.5	1413.0	1640.0	1873.6	2059.8	2058.4
45°	880.4	904.9	934.8	962.0	1006.8	1078.8	1232.3	1402.2	1626.4	1837.0	1919.8
47.5°	786.7	809.8	839.7	847.8	877.7	945.7	1039.4	1187.5	1396.7	1606.0	1762.2
50°	707.9	726.9	747.3	762.2	775.8	831.5	902.2	1027.2	1194.3	1396.7	1591.0
52.5°	646.7	660.3	678.0	686.1	698.4	739.1	793.5	885.9	1023.1	1207.9	1396.7
55°	589.7	599.2	610.1	623.6	629.1	659.0	701.1	779.9	881.8	1047.6	1226.9
57.5°	536.7	540.8	547.6	555.7	562.5	588.3	625.0	678.0	767.7	895.4	1065.2
60°	476.9	487.8	491.8	500.0	504.1	524.5	553.0	597.8	667.1	777.2	904.9
62.5°	426.6	433.4	440.2	444.3	453.8	460.6	483.7	524.5	581.5	663.0	778.5
65°	381.8	384.5	388.6	392.7	395.4	403.5	425.3	452.4	495.9	567.9	657.6
67.5°	330.2	332.9	338.3	339.7	342.4	353.3	365.5	388.6	425.3	479.6	553.0
70°	279.9	284.0	286.7	289.4	293.5	297.6	311.1	330.2	358.7	396.7	453.8
72.5°	236.4	240.5	240.5	243.2	241.8	247.3	260.9	274.5	293.5	324.7	375.0
75°	192.9	192.9	195.7	197.0	198.4	203.8	209.2	220.1	235.1	259.5	290.8
77.5°	152.2	150.8	153.5	153.5	153.5	157.6	163.0	168.5	178.0	195.7	220.1
80°	111.4	111.4	114.1	115.5	112.8	114.1	116.8	122.3	129.1	141.3	154.9
82.5°	73.4	78.8	77.4	78.8	77.4	80.2	81.5	82.9	85.6	91.0	100.5
85°	44.8	44.8	44.8	46.2	44.8	46.2	46.2	46.2	47.6	50.3	54.3
87.5°	19.0	19.0	19.0	20.4	19.0	19.0	20.4	19.0	20.4	20.4	21.7
90°	28.8	27.8	28.8	27.8	26.8	25.8	24.8	23.8	24.8	21.8	18.9
92.5°	53.6	57.6	59.6	63.0	66.5	76.4	98.3	138.0	184.6	204.5	152.9
95°	126.1	135.0	153.8	171.7	189.6	242.2	357.3	477.4	588.6	524.1	361.3
97.5°	271.0	308.7	375.2	431.8	488.3	619.4	820.9	936.0	905.2	675.9	402.0
100°	660.1	732.5	832.8	903.2	973.7	1089.8	1170.2	1135.5	940.0	635.2	374.2
102.5°	1045.2	1098.8	1171.2	1209.4	1247.7	1303.2	1286.4	1145.4	875.4	575.7	350.4
105°	1299.3	1337.0	1382.6	1395.5	1408.4	1389.6	1290.3	1082.9	798.0	529.0	341.4
107.5°	1467.0	1484.9	1490.8	1477.4	1464.0	1386.6	1230.8	993.6	729.5	495.3	339.5
110°	1550.4	1542.4	1514.7	1480.0	1445.2	1320.1	1137.5	910.2	673.0	477.4	344.4

TEST NUMBER: P1011039

CATALOG NUMBER: S123DIP-B1000D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1556.3	1527.6	1471.0	1423.8	1376.7	1232.8	1045.2	837.7	635.2	467.5	354.3
115°	1510.7	1467.0	1392.6	1338.5	1284.4	1138.5	965.8	782.1	610.4	466.5	365.3
117.5°	1429.3	1380.7	1303.2	1247.2	1191.1	1057.1	904.2	745.4	593.6	467.5	379.2
120°	1344.9	1289.3	1210.9	1160.8	1110.7	991.6	857.6	717.6	582.6	471.5	395.0
122.5°	1254.6	1206.0	1138.5	1092.8	1047.2	939.0	820.9	694.8	575.7	478.4	409.9
125°	1179.2	1135.5	1072.0	1032.3	992.6	897.3	789.1	675.9	569.7	485.4	425.8
127.5°	1114.6	1076.9	1019.4	982.6	945.9	858.6	760.3	658.1	566.8	493.3	438.7
130°	1059.1	1023.3	970.7	937.0	903.2	822.8	733.5	644.2	563.8	501.2	451.6
132.5°	1010.4	974.7	926.1	894.3	862.5	789.1	708.7	631.3	562.8	507.2	463.5
135°	956.8	927.1	878.4	850.1	821.8	757.3	686.9	620.4	561.8	513.2	473.5
137.5°	906.2	875.4	833.8	808.4	783.1	725.6	666.0	610.4	559.8	517.1	481.4
140°	854.6	826.8	789.1	767.8	746.4	698.8	648.1	601.5	558.8	521.1	487.3
142.5°	803.0	779.2	748.4	730.6	712.7	673.0	631.3	593.6	556.8	524.1	493.3
145°	757.3	736.5	711.7	697.3	682.9	651.1	618.4	586.6	554.8	525.1	497.3
147.5°	716.6	701.7	681.9	671.4	661.0	634.2	607.4	579.7	551.9	525.1	500.3
150°	683.9	673.0	658.1	648.7	639.2	618.4	595.5	572.7	547.9	525.1	501.2
152.5°	657.1	647.2	636.2	628.8	621.3	603.5	584.6	564.8	542.9	522.1	503.2
155°	633.3	625.3	616.4	610.4	604.5	589.6	573.7	556.8	537.0	520.1	503.2
157.5°	611.4	605.5	597.5	592.6	587.6	575.7	561.8	547.9	532.0	517.1	504.2
160°	592.6	586.6	579.7	576.2	572.7	562.8	551.9	539.0	526.1	515.1	504.2
162.5°	572.7	567.7	563.8	560.8	557.8	548.9	540.0	530.0	520.1	511.2	503.2
165°	555.8	551.9	547.9	545.4	542.9	536.0	530.0	522.1	514.1	507.2	501.2
167.5°	539.0	536.0	534.0	532.0	530.0	526.1	521.1	514.1	508.2	503.2	500.3
170°	524.1	522.1	521.1	520.1	519.1	515.1	512.2	507.2	502.2	499.3	497.3
172.5°	512.2	510.2	510.2	509.7	509.2	506.2	504.2	500.3	497.3	496.3	496.3
175°	501.2	500.3	500.3	500.3	500.3	498.3	497.3	495.3	493.3	493.3	494.3
177.5°	494.3	493.3	494.3	494.3	494.3	493.3	492.3	491.3	490.3	491.3	493.3
180°	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3

TEST NUMBER: P1011039

CATALOG NUMBER: S123DIP-B1000D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2
2.5°	1440.2	1436.1	1436.1	1433.4	1425.3	1410.3	1409.0	1411.7	1403.5	1395.4	1383.2
5°	1510.9	1485.1	1476.9	1468.8	1452.5	1425.3	1414.4	1404.9	1390.0	1372.3	1353.3
7.5°	1570.7	1534.0	1523.1	1508.2	1475.5	1437.5	1413.0	1392.7	1372.3	1347.8	1324.7
10°	1645.4	1592.4	1566.6	1544.8	1500.0	1447.0	1410.3	1380.4	1347.8	1317.9	1288.0
12.5°	1729.6	1644.0	1635.9	1582.9	1531.3	1452.5	1407.6	1364.1	1320.7	1284.0	1252.7
15°	1800.3	1706.5	1672.6	1637.2	1538.0	1440.2	1396.7	1347.8	1297.6	1258.2	1212.0
17.5°	1845.1	1767.7	1695.7	1648.1	1544.8	1457.9	1373.6	1317.9	1264.9	1210.6	1172.6
20°	1899.5	1786.7	1724.2	1660.3	1558.4	1444.3	1360.1	1290.8	1225.5	1176.6	1130.4
22.5°	1953.8	1801.6	1750.0	1680.7	1561.1	1430.7	1335.6	1266.3	1191.6	1142.7	1092.4
25°	1948.4	1823.4	1737.8	1679.4	1534.0	1418.5	1307.1	1225.5	1156.3	1093.8	1043.5
27.5°	1952.5	1798.9	1712.0	1644.0	1515.0	1400.8	1277.2	1191.6	1119.6	1054.4	1001.4
30°	1953.8	1762.2	1686.1	1604.6	1479.6	1358.7	1243.2	1156.3	1080.2	1009.5	962.0
32.5°	1949.7	1732.3	1637.2	1563.9	1423.9	1317.9	1203.8	1111.4	1034.0	968.8	923.9
35°	1940.2	1697.0	1587.0	1494.6	1366.9	1259.5	1167.1	1072.0	989.1	929.4	877.7
37.5°	1914.4	1659.0	1534.0	1442.9	1300.3	1191.6	1110.1	1031.3	951.1	880.4	837.0
40°	1895.4	1607.3	1481.0	1381.8	1228.3	1122.3	1054.4	979.6	900.8	837.0	794.8
42.5°	1851.9	1558.4	1426.6	1308.4	1157.6	1048.9	985.1	925.3	857.3	794.8	756.8
45°	1781.3	1505.4	1360.1	1240.5	1080.2	976.9	918.5	869.6	809.8	750.0	712.0
47.5°	1682.1	1429.4	1289.4	1169.8	1004.1	899.5	841.0	804.4	756.8	706.5	673.9
50°	1574.7	1346.5	1217.4	1099.2	930.7	828.8	771.7	737.8	706.5	660.3	629.1
52.5°	1434.8	1258.2	1134.5	1021.7	851.9	754.1	703.8	679.4	646.7	614.1	587.0
55°	1298.9	1144.0	1042.1	934.8	774.5	683.4	634.5	608.7	589.7	562.5	540.8
57.5°	1141.3	1038.0	944.3	846.5	702.4	619.6	573.4	542.1	529.9	517.7	497.3
60°	995.9	917.1	841.0	759.5	627.7	553.0	508.2	483.7	471.5	463.3	449.7
62.5°	862.8	801.6	736.4	671.2	551.6	483.7	449.7	425.3	414.4	413.0	400.8
65°	735.1	691.6	638.6	574.7	481.0	421.2	388.6	373.6	361.4	361.4	351.9
67.5°	607.3	577.4	535.3	490.5	417.1	361.4	331.5	317.9	311.1	311.1	304.3
70°	505.4	485.1	447.0	407.6	343.8	301.6	278.5	266.3	262.2	263.6	258.2
72.5°	410.3	388.6	357.3	328.8	281.3	250.0	233.7	220.1	213.3	214.7	213.3
75°	317.9	307.1	279.9	258.2	220.1	198.4	183.4	176.6	171.2	172.6	169.8
77.5°	239.1	222.8	207.9	192.9	169.8	152.2	139.9	133.2	129.1	129.1	129.1
80°	163.0	160.3	148.1	139.9	120.9	107.3	97.8	96.5	92.4	92.4	92.4
82.5°	106.0	99.2	92.4	87.0	76.1	67.9	63.9	61.1	59.8	58.4	61.1
85°	58.4	54.3	51.6	46.2	42.1	38.0	34.0	32.6	31.3	32.6	31.3
87.5°	23.1	19.0	19.0	17.7	16.3	14.9	14.9	12.2	12.2	10.9	10.9
90°	15.9	12.9	11.9	10.9	8.9	6.0	4.0	2.0	4.0	6.0	8.9
92.5°	100.2	68.5	59.6	50.6	40.7	31.8	21.8	14.9	21.8	31.8	40.7
95°	213.4	129.0	109.6	90.3	64.5	47.6	36.7	33.7	36.7	47.6	64.5
97.5°	230.3	146.9	125.6	104.2	78.4	63.5	54.6	53.6	54.6	63.5	78.4
100°	227.3	157.8	138.4	119.1	95.3	81.4	74.4	73.4	74.4	81.4	95.3
102.5°	231.3	170.7	153.4	136.0	115.1	102.2	96.3	94.3	96.3	102.2	115.1
105°	239.2	185.6	170.2	154.8	136.0	124.1	118.1	115.1	118.1	124.1	136.0
107.5°	252.1	204.5	190.1	175.7	157.8	145.9	140.0	137.0	140.0	145.9	157.8
110°	269.0	224.3	210.4	196.5	179.7	168.7	163.8	160.8	163.8	168.7	179.7

TEST NUMBER: P1011039

CATALOG NUMBER: S123DIP-B1000D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	285.9	245.2	231.8	218.4	201.5	190.6	185.6	182.6	185.6	190.6	201.5
115°	304.7	267.0	253.6	240.2	223.3	213.4	207.4	203.5	207.4	213.4	223.3
117.5°	324.6	286.9	274.4	262.0	243.2	234.2	229.3	224.3	229.3	234.2	243.2
120°	343.4	307.7	295.3	282.9	264.0	254.1	249.1	246.2	249.1	254.1	264.0
122.5°	363.3	328.5	315.1	301.7	283.9	273.0	268.0	265.0	268.0	273.0	283.9
125°	382.1	347.4	334.0	320.6	301.7	290.8	284.9	282.9	284.9	290.8	301.7
127.5°	399.0	365.3	351.9	338.5	317.6	306.7	299.8	296.8	299.8	306.7	317.6
130°	413.9	381.1	367.7	354.3	333.5	321.6	312.7	309.7	312.7	321.6	333.5
132.5°	426.8	395.0	382.1	369.2	348.4	333.5	323.6	319.6	323.6	333.5	348.4
135°	439.7	408.9	395.5	382.1	361.3	346.4	335.5	331.5	335.5	346.4	361.3
137.5°	448.6	418.9	406.4	394.0	373.2	357.3	346.4	342.4	346.4	357.3	373.2
140°	457.6	428.8	416.4	404.0	384.1	368.2	358.3	353.4	358.3	368.2	384.1
142.5°	464.5	436.7	425.3	413.9	394.0	380.2	369.2	365.3	369.2	380.2	394.0
145°	470.5	444.7	433.2	421.8	405.0	390.1	381.1	378.2	381.1	390.1	405.0
147.5°	475.4	451.6	441.7	431.8	414.9	402.0	393.1	391.1	393.1	402.0	414.9
150°	480.4	457.6	448.6	439.7	425.8	412.9	405.0	404.0	405.0	412.9	425.8
152.5°	483.4	464.5	456.0	447.6	435.7	424.8	416.9	416.9	416.9	424.8	435.7
155°	487.3	470.5	463.6	456.6	445.7	435.7	429.8	429.8	429.8	435.7	445.7
157.5°	489.3	475.4	470.0	464.5	454.6	445.7	440.7	439.7	440.7	445.7	454.6
160°	492.3	480.4	475.4	470.5	463.5	455.6	451.6	451.6	451.6	455.6	463.5
162.5°	493.3	483.4	479.4	475.4	469.5	463.5	460.5	460.5	460.5	463.5	469.5
165°	494.3	486.4	482.9	479.4	475.4	470.5	468.5	469.5	468.5	470.5	475.4
167.5°	494.3	488.3	485.8	483.4	480.4	476.4	475.4	476.4	475.4	476.4	480.4
170°	493.3	488.3	487.4	486.4	484.4	481.4	480.4	482.4	480.4	481.4	484.4
172.5°	493.3	489.3	488.8	488.3	487.3	485.4	485.4	486.4	485.4	485.4	487.3
175°	492.3	490.3	489.8	489.3	489.3	487.3	488.3	489.3	488.3	487.3	489.3
177.5°	491.3	490.3	490.3	490.3	490.3	489.3	490.3	491.3	490.3	489.3	490.3
180°	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3

TEST NUMBER: P1011039

CATALOG NUMBER: S123DIP-B1000D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2
2.5°	1380.4	1379.1	1381.8	1373.6	1360.1	1353.3	1334.2	1330.2	1328.8	1330.2	1331.5
5°	1342.4	1341.0	1337.0	1323.4	1307.1	1294.8	1271.7	1270.4	1262.2	1254.1	1258.2
7.5°	1305.7	1300.3	1292.1	1274.5	1252.7	1239.1	1220.1	1206.5	1195.7	1188.9	1183.4
10°	1269.0	1260.9	1252.7	1229.6	1202.4	1182.1	1159.0	1148.1	1135.9	1130.4	1125.0
12.5°	1221.5	1213.3	1198.4	1171.2	1154.9	1129.1	1106.0	1095.1	1088.3	1077.4	1070.7
15°	1183.4	1167.1	1159.0	1130.4	1096.5	1093.8	1051.6	1048.9	1035.3	1035.3	1024.5
17.5°	1139.9	1127.7	1112.8	1084.2	1059.8	1035.3	1013.6	1005.4	993.2	990.5	985.1
20°	1097.8	1081.5	1076.1	1047.6	1021.7	991.9	968.8	960.6	955.2	949.7	953.8
22.5°	1054.4	1040.8	1027.2	1001.4	982.3	952.4	938.9	930.7	922.6	919.8	921.2
25°	1012.2	1000.0	986.4	960.6	940.2	915.8	903.5	899.5	895.4	895.4	894.0
27.5°	971.5	959.2	947.0	923.9	903.5	885.9	876.4	872.3	868.2	870.9	873.6
30°	929.4	918.5	907.6	887.2	870.9	854.6	849.2	846.5	845.1	851.9	851.9
32.5°	891.3	881.8	873.6	854.6	838.3	824.7	820.7	822.0	823.4	827.4	830.2
35°	851.9	845.1	837.0	820.7	807.1	794.8	796.2	796.2	798.9	805.7	811.1
37.5°	816.6	807.1	800.3	786.7	775.8	764.9	769.0	773.1	775.8	784.0	786.7
40°	774.5	770.4	764.9	751.4	741.9	740.5	741.9	744.6	750.0	754.1	758.2
42.5°	740.5	735.1	728.3	717.4	709.2	710.6	712.0	714.7	717.4	724.2	728.3
45°	702.4	698.4	692.9	683.4	676.6	678.0	679.4	679.4	682.1	690.2	692.9
47.5°	660.3	661.7	654.9	645.4	641.3	641.3	641.3	644.0	650.8	653.5	654.9
50°	619.6	616.8	615.5	606.0	603.3	601.9	603.3	604.6	614.1	612.8	616.8
52.5°	576.1	576.1	574.7	569.3	565.2	565.2	562.5	569.3	572.0	574.7	578.8
55°	534.0	529.9	528.5	525.8	520.4	519.0	521.7	529.9	532.6	535.3	539.4
57.5°	487.8	487.8	485.1	481.0	481.0	481.0	481.0	486.4	490.5	493.2	501.4
60°	445.7	440.2	436.1	436.1	436.1	434.8	442.9	442.9	451.1	452.4	455.2
62.5°	395.4	392.7	389.9	391.3	389.9	392.7	395.4	400.8	402.2	406.3	410.3
65°	347.8	347.8	345.1	353.3	347.8	347.8	354.6	354.6	357.3	361.4	366.8
67.5°	301.6	303.0	300.3	300.3	303.0	304.3	305.7	311.1	312.5	317.9	324.7
70°	254.1	256.8	258.2	255.4	258.2	260.9	263.6	264.9	270.4	273.1	277.2
72.5°	212.0	214.7	210.6	212.0	213.3	216.0	217.4	220.1	222.8	231.0	233.7
75°	169.8	168.5	167.1	172.6	169.8	175.3	176.6	176.6	179.3	186.1	188.9
77.5°	130.4	130.4	131.8	129.1	133.2	131.8	133.2	137.2	141.3	141.3	152.2
80°	91.0	93.8	93.8	93.8	95.1	96.5	93.8	100.5	101.9	101.9	106.0
82.5°	58.4	59.8	58.4	61.1	61.1	63.9	62.5	63.9	66.6	69.3	70.7
85°	31.3	31.3	34.0	34.0	32.6	34.0	32.6	34.0	36.7	36.7	38.0
87.5°	10.9	10.9	10.9	10.9	12.2	10.9	12.2	12.2	10.9	10.9	14.9
90°	10.9	11.9	12.9	15.9	18.9	21.8	24.8	23.8	24.8	25.8	26.8
92.5°	50.6	59.6	68.5	100.2	152.9	204.5	184.6	138.0	98.3	76.4	66.5
95°	90.3	109.6	129.0	213.4	361.3	524.1	588.6	477.4	357.3	242.2	189.6
97.5°	104.2	125.6	146.9	230.3	402.0	675.9	905.2	936.0	820.9	619.4	488.3
100°	119.1	138.4	157.8	227.3	374.2	635.2	940.0	1135.5	1170.2	1089.8	973.7
102.5°	136.0	153.4	170.7	231.3	350.4	575.7	875.4	1145.4	1286.4	1303.2	1247.7
105°	154.8	170.2	185.6	239.2	341.4	529.0	798.0	1082.9	1290.3	1389.6	1408.4
107.5°	175.7	190.1	204.5	252.1	339.5	495.3	729.5	993.6	1230.8	1386.6	1464.0
110°	196.5	210.4	224.3	269.0	344.4	477.4	673.0	910.2	1137.5	1320.1	1445.2

TEST NUMBER: P1011039

CATALOG NUMBER: S123DIP-B1000D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	218.4	231.8	245.2	285.9	354.3	467.5	635.2	837.7	1045.2	1232.8	1376.7
115°	240.2	253.6	267.0	304.7	365.3	466.5	610.4	782.1	965.8	1138.5	1284.4
117.5°	262.0	274.4	286.9	324.6	379.2	467.5	593.6	745.4	904.2	1057.1	1191.1
120°	282.9	295.3	307.7	343.4	395.0	471.5	582.6	717.6	857.6	991.6	1110.7
122.5°	301.7	315.1	328.5	363.3	409.9	478.4	575.7	694.8	820.9	939.0	1047.2
125°	320.6	334.0	347.4	382.1	425.8	485.4	569.7	675.9	789.1	897.3	992.6
127.5°	338.5	351.9	365.3	399.0	438.7	493.3	566.8	658.1	760.3	858.6	945.9
130°	354.3	367.7	381.1	413.9	451.6	501.2	563.8	644.2	733.5	822.8	903.2
132.5°	369.2	382.1	395.0	426.8	463.5	507.2	562.8	631.3	708.7	789.1	862.5
135°	382.1	395.5	408.9	439.7	473.5	513.2	561.8	620.4	686.9	757.3	821.8
137.5°	394.0	406.4	418.9	448.6	481.4	517.1	559.8	610.4	666.0	725.6	783.1
140°	404.0	416.4	428.8	457.6	487.3	521.1	558.8	601.5	648.1	698.8	746.4
142.5°	413.9	425.3	436.7	464.5	493.3	524.1	556.8	593.6	631.3	673.0	712.7
145°	421.8	433.2	444.7	470.5	497.3	525.1	554.8	586.6	618.4	651.1	682.9
147.5°	431.8	441.7	451.6	475.4	500.3	525.1	551.9	579.7	607.4	634.2	661.0
150°	439.7	448.6	457.6	480.4	501.2	525.1	547.9	572.7	595.5	618.4	639.2
152.5°	447.6	456.0	464.5	483.4	503.2	522.1	542.9	564.8	584.6	603.5	621.3
155°	456.6	463.6	470.5	487.3	503.2	520.1	537.0	556.8	573.7	589.6	604.5
157.5°	464.5	470.0	475.4	489.3	504.2	517.1	532.0	547.9	561.8	575.7	587.6
160°	470.5	475.4	480.4	492.3	504.2	515.1	526.1	539.0	551.9	562.8	572.7
162.5°	475.4	479.4	483.4	493.3	503.2	511.2	520.1	530.0	540.0	548.9	557.8
165°	479.4	482.9	486.4	494.3	501.2	507.2	514.1	522.1	530.0	536.0	542.9
167.5°	483.4	485.8	488.3	494.3	500.3	503.2	508.2	514.1	521.1	526.1	530.0
170°	486.4	487.4	488.3	493.3	497.3	499.3	502.2	507.2	512.2	515.1	519.1
172.5°	488.3	488.8	489.3	493.3	496.3	496.3	497.3	500.3	504.2	506.2	509.2
175°	489.3	489.8	490.3	492.3	494.3	493.3	493.3	495.3	497.3	498.3	500.3
177.5°	490.3	490.3	490.3	491.3	493.3	491.3	490.3	491.3	492.3	493.3	494.3
180°	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3

TEST NUMBER: P1011039

CATALOG NUMBER: S123DIP-B1000D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2
2.5°	1330.2	1331.5	1326.1	1322.0	1332.9	1326.1	1326.1	1327.5	1324.7	1328.8	1327.5
5°	1255.4	1256.8	1247.3	1250.0	1244.6	1243.2	1241.9	1250.0	1248.6	1247.3	1250.0
7.5°	1182.1	1182.1	1178.0	1175.3	1175.3	1171.2	1176.6	1175.3	1178.0	1178.0	1182.1
10°	1120.9	1123.6	1116.9	1110.1	1108.7	1110.1	1110.1	1111.4	1112.8	1122.3	1120.9
12.5°	1070.7	1066.6	1065.2	1061.1	1054.4	1051.6	1048.9	1063.9	1059.8	1059.8	1059.8
15°	1014.9	1024.5	1023.1	1010.9	1008.2	1013.6	1010.9	1010.9	1024.5	1023.1	1021.7
17.5°	985.1	982.3	979.6	972.8	974.2	972.8	974.2	974.2	982.3	982.3	982.3
20°	951.1	945.7	945.7	942.9	942.9	938.9	944.3	945.7	951.1	951.1	952.4
22.5°	921.2	917.1	917.1	915.8	918.5	913.0	918.5	919.8	919.8	923.9	923.9
25°	895.4	892.7	892.7	895.4	895.4	895.4	895.4	900.8	896.7	898.1	896.7
27.5°	872.3	873.6	875.0	876.4	875.0	876.4	877.7	880.4	881.8	880.4	877.7
30°	850.5	854.6	856.0	856.0	858.7	860.1	861.4	861.4	862.8	858.7	861.4
32.5°	834.2	834.2	837.0	838.3	841.0	842.4	842.4	845.1	843.8	839.7	841.0
35°	811.1	811.1	816.6	819.3	823.4	822.0	823.4	823.4	824.7	822.0	817.9
37.5°	788.0	790.8	790.8	796.2	797.6	798.9	797.6	800.3	798.9	796.2	794.8
40°	760.9	759.5	760.9	764.9	766.3	766.3	766.3	769.0	769.0	769.0	767.7
42.5°	726.9	731.0	729.6	733.7	732.3	732.3	735.1	737.8	739.1	735.1	736.4
45°	694.3	694.3	697.0	697.0	698.4	698.4	703.8	701.1	703.8	701.1	702.4
47.5°	659.0	660.3	660.3	661.7	664.4	667.1	664.4	665.8	665.8	667.1	664.4
50°	619.6	619.6	622.3	626.4	631.8	629.1	627.7	633.2	629.1	629.1	626.4
52.5°	578.8	582.9	584.2	588.3	592.4	593.8	595.1	592.4	593.8	589.7	591.0
55°	539.4	540.8	546.2	550.3	554.3	554.3	553.0	554.3	555.7	550.3	550.3
57.5°	500.0	504.1	509.5	509.5	514.9	514.9	513.6	513.6	514.9	510.9	509.5
60°	457.9	462.0	468.8	468.8	476.9	478.3	475.5	472.8	472.8	468.8	470.1
62.5°	413.0	417.1	421.2	428.0	433.4	430.7	436.1	430.7	432.1	423.9	423.9
65°	373.6	375.0	381.8	388.6	388.6	391.3	388.6	389.9	385.9	385.9	380.4
67.5°	327.4	327.4	334.2	341.0	347.8	347.8	347.8	343.8	343.8	339.7	339.7
70°	286.7	285.3	292.1	296.2	300.3	301.6	298.9	297.6	294.8	290.8	289.4
72.5°	236.4	239.1	245.9	248.6	255.4	254.1	260.9	252.7	252.7	245.9	244.6
75°	191.6	194.3	201.1	205.2	209.2	209.2	213.3	209.2	203.8	201.1	199.7
77.5°	152.2	150.8	156.3	163.0	164.4	163.0	165.8	164.4	159.0	159.0	156.3
80°	108.7	112.8	118.2	116.8	122.3	120.9	120.9	118.2	118.2	114.1	116.8
82.5°	72.0	76.1	77.4	76.1	77.4	80.2	81.5	80.2	80.2	77.4	78.8
85°	38.0	38.0	40.8	42.1	40.8	40.8	42.1	46.2	43.5	40.8	43.5
87.5°	12.2	10.9	10.9	12.2	10.9	10.9	12.2	12.2	13.6	13.6	13.6
90°	27.8	28.8	27.8	28.8	29.8	28.8	29.8	28.8	27.8	28.8	27.8
92.5°	63.0	59.6	57.6	53.6	54.6	52.6	54.6	53.6	57.6	59.6	63.0
95°	171.7	153.8	135.0	126.1	119.1	115.1	119.1	126.1	135.0	153.8	171.7
97.5°	431.8	375.2	308.7	271.0	247.1	236.2	247.1	271.0	308.7	375.2	431.8
100°	903.2	832.8	732.5	660.1	621.3	622.3	621.3	660.1	732.5	832.8	903.2
102.5°	1209.4	1171.2	1098.8	1045.2	1014.4	985.6	1014.4	1045.2	1098.8	1171.2	1209.4
105°	1395.5	1382.6	1337.0	1299.3	1267.5	1262.5	1267.5	1299.3	1337.0	1382.6	1395.5
107.5°	1477.4	1490.8	1484.9	1467.0	1454.1	1443.2	1454.1	1467.0	1484.9	1490.8	1477.4
110°	1480.0	1514.7	1542.4	1550.4	1548.4	1546.4	1548.4	1550.4	1542.4	1514.7	1480.0

TEST NUMBER: P1011039

CATALOG NUMBER: S123DIP-B1000D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1423.8	1471.0	1527.6	1556.3	1566.3	1567.3	1566.3	1556.3	1527.6	1471.0	1423.8
115°	1338.5	1392.6	1467.0	1510.7	1530.5	1535.5	1530.5	1510.7	1467.0	1392.6	1338.5
117.5°	1247.2	1303.2	1380.7	1429.3	1459.1	1466.0	1459.1	1429.3	1380.7	1303.2	1247.2
120°	1160.8	1210.9	1289.3	1344.9	1368.7	1374.7	1368.7	1344.9	1289.3	1210.9	1160.8
122.5°	1092.8	1138.5	1206.0	1254.6	1281.4	1289.3	1281.4	1254.6	1206.0	1138.5	1092.8
125°	1032.3	1072.0	1135.5	1179.2	1204.0	1210.9	1204.0	1179.2	1135.5	1072.0	1032.3
127.5°	982.6	1019.4	1076.9	1114.6	1137.5	1143.4	1137.5	1114.6	1076.9	1019.4	982.6
130°	937.0	970.7	1023.3	1059.1	1079.9	1087.8	1079.9	1059.1	1023.3	970.7	937.0
132.5°	894.3	926.1	974.7	1010.4	1028.3	1033.3	1028.3	1010.4	974.7	926.1	894.3
135°	850.1	878.4	927.1	956.8	974.7	981.6	974.7	956.8	927.1	878.4	850.1
137.5°	808.4	833.8	875.4	906.2	921.1	927.1	921.1	906.2	875.4	833.8	808.4
140°	767.8	789.1	826.8	854.6	870.5	869.5	870.5	854.6	826.8	789.1	767.8
142.5°	730.6	748.4	779.2	803.0	816.9	815.9	816.9	803.0	779.2	748.4	730.6
145°	697.3	711.7	736.5	757.3	765.3	767.3	765.3	757.3	736.5	711.7	697.3
147.5°	671.4	681.9	701.7	716.6	724.6	725.6	724.6	716.6	701.7	681.9	671.4
150°	648.7	658.1	673.0	683.9	689.8	689.8	689.8	683.9	673.0	658.1	648.7
152.5°	628.8	636.2	647.2	657.1	660.1	660.1	660.1	657.1	647.2	636.2	628.8
155°	610.4	616.4	625.3	633.3	635.2	636.2	635.2	633.3	625.3	616.4	610.4
157.5°	592.6	597.5	605.5	611.4	613.4	613.4	613.4	611.4	605.5	597.5	592.6
160°	576.2	579.7	586.6	592.6	592.6	591.6	592.6	592.6	586.6	579.7	576.2
162.5°	560.8	563.8	567.7	572.7	572.7	571.7	572.7	572.7	567.7	563.8	560.8
165°	545.4	547.9	551.9	555.8	554.8	554.8	554.8	555.8	551.9	547.9	545.4
167.5°	532.0	534.0	536.0	539.0	538.0	538.0	538.0	539.0	536.0	534.0	532.0
170°	520.1	521.1	522.1	524.1	523.1	523.1	523.1	524.1	522.1	521.1	520.1
172.5°	509.7	510.2	510.2	512.2	510.2	509.2	510.2	512.2	510.2	510.2	509.7
175°	500.3	500.3	500.3	501.2	500.3	499.3	500.3	501.2	500.3	500.3	500.3
177.5°	494.3	494.3	493.3	494.3	492.3	492.3	492.3	494.3	493.3	494.3	494.3
180°	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3

TEST NUMBER: P1011039

CATALOG NUMBER: S123DIP-B1000D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2	1402.2
2.5°	1331.5	1334.2	1335.6	1330.2	1326.1	1332.9	1342.4	1349.2	1354.6	1361.4	1365.5
5°	1252.7	1262.2	1262.2	1264.9	1269.0	1275.8	1293.5	1305.7	1316.6	1324.7	1331.5
7.5°	1186.1	1192.9	1197.0	1203.8	1210.6	1220.1	1240.5	1258.2	1274.5	1284.0	1294.8
10°	1126.4	1131.8	1138.6	1142.7	1154.9	1168.5	1194.3	1209.2	1228.3	1243.2	1256.8
12.5°	1069.3	1088.3	1092.4	1091.0	1101.9	1116.9	1142.7	1165.8	1186.1	1201.1	1216.0
15°	1028.5	1035.3	1043.5	1042.1	1065.2	1069.3	1091.0	1118.2	1145.4	1154.9	1168.5
17.5°	983.7	994.6	1002.7	1006.8	1013.6	1028.5	1048.9	1069.3	1104.6	1106.0	1141.3
20°	948.4	959.2	964.7	970.1	974.2	991.9	1009.5	1032.6	1061.1	1076.1	1095.1
22.5°	925.3	930.7	934.8	938.9	944.3	953.8	975.5	1001.4	1020.4	1036.7	1048.9
25°	898.1	903.5	909.0	911.7	915.8	921.2	937.5	957.9	985.1	995.9	1008.2
27.5°	879.1	879.1	881.8	881.8	887.2	892.7	904.9	923.9	945.7	959.2	975.5
30°	858.7	857.3	858.7	857.3	856.0	864.1	875.0	891.3	906.3	922.6	933.4
32.5°	838.3	837.0	837.0	838.3	832.9	837.0	842.4	857.3	873.6	881.8	894.0
35°	816.6	813.9	813.9	813.9	811.1	808.4	813.9	827.4	838.3	849.2	858.7
37.5°	794.8	790.8	790.8	788.0	785.3	781.3	781.3	792.1	807.1	811.1	823.4
40°	764.9	764.9	762.2	760.9	758.2	755.4	751.4	760.9	774.5	778.5	788.0
42.5°	735.1	731.0	729.6	729.6	729.6	725.5	722.8	729.6	737.8	744.6	750.0
45°	701.1	698.4	699.7	698.4	695.7	694.3	692.9	695.7	705.2	707.9	714.7
47.5°	664.4	663.0	663.0	661.7	660.3	661.7	656.3	663.0	665.8	668.5	673.9
50°	626.4	625.0	623.6	622.3	622.3	623.6	622.3	622.3	627.7	630.4	635.9
52.5°	588.3	584.2	584.2	582.9	582.9	580.2	582.9	584.2	587.0	589.7	592.4
55°	547.6	547.6	543.5	543.5	540.8	540.8	542.1	540.8	546.2	548.9	548.9
57.5°	508.2	502.7	504.1	501.4	498.6	497.3	497.3	500.0	502.7	502.7	505.4
60°	466.0	460.6	459.2	453.8	456.5	452.4	453.8	453.8	459.2	456.5	459.2
62.5°	423.9	417.1	413.0	410.3	410.3	411.7	409.0	407.6	410.3	413.0	418.5
65°	379.1	375.0	370.9	366.8	366.8	365.5	368.2	364.1	362.8	364.1	366.8
67.5°	332.9	328.8	324.7	320.7	322.0	317.9	315.2	319.3	316.6	317.9	320.7
70°	288.0	285.3	277.2	274.5	273.1	274.5	273.1	270.4	274.5	273.1	274.5
72.5°	243.2	240.5	236.4	229.6	229.6	228.3	226.9	226.9	225.5	225.5	225.5
75°	199.7	194.3	190.2	188.9	186.1	184.8	183.4	180.7	182.1	183.4	180.7
77.5°	154.9	148.1	146.7	146.7	142.7	142.7	144.0	142.7	141.3	141.3	141.3
80°	114.1	108.7	108.7	106.0	103.3	103.3	103.3	103.3	101.9	100.5	101.9
82.5°	73.4	72.0	70.7	70.7	73.4	67.9	70.7	69.3	67.9	67.9	66.6
85°	40.8	42.1	40.8	42.1	39.4	40.8	40.8	40.8	39.4	40.8	38.0
87.5°	14.9	14.9	14.9	16.3	16.3	16.3	16.3	16.3	17.7	16.3	16.3
90°	26.8	25.8	24.8	23.8	24.8	21.8	18.9	15.9	12.9	11.9	10.9
92.5°	66.5	76.4	98.3	138.0	184.6	204.5	152.9	100.2	68.5	59.6	50.6
95°	189.6	242.2	357.3	477.4	588.6	524.1	361.3	213.4	129.0	109.6	90.3
97.5°	488.3	619.4	820.9	936.0	905.2	675.9	402.0	230.3	146.9	125.6	104.2
100°	973.7	1089.8	1170.2	1135.5	940.0	635.2	374.2	227.3	157.8	138.4	119.1
102.5°	1247.7	1303.2	1286.4	1145.4	875.4	575.7	350.4	231.3	170.7	153.4	136.0
105°	1408.4	1389.6	1290.3	1082.9	798.0	529.0	341.4	239.2	185.6	170.2	154.8
107.5°	1464.0	1386.6	1230.8	993.6	729.5	495.3	339.5	252.1	204.5	190.1	175.7
110°	1445.2	1320.1	1137.5	910.2	673.0	477.4	344.4	269.0	224.3	210.4	196.5

TEST NUMBER: P1011039

CATALOG NUMBER: S123DIP-B1000D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1376.7	1232.8	1045.2	837.7	635.2	467.5	354.3	285.9	245.2	231.8	218.4
115°	1284.4	1138.5	965.8	782.1	610.4	466.5	365.3	304.7	267.0	253.6	240.2
117.5°	1191.1	1057.1	904.2	745.4	593.6	467.5	379.2	324.6	286.9	274.4	262.0
120°	1110.7	991.6	857.6	717.6	582.6	471.5	395.0	343.4	307.7	295.3	282.9
122.5°	1047.2	939.0	820.9	694.8	575.7	478.4	409.9	363.3	328.5	315.1	301.7
125°	992.6	897.3	789.1	675.9	569.7	485.4	425.8	382.1	347.4	334.0	320.6
127.5°	945.9	858.6	760.3	658.1	566.8	493.3	438.7	399.0	365.3	351.9	338.5
130°	903.2	822.8	733.5	644.2	563.8	501.2	451.6	413.9	381.1	367.7	354.3
132.5°	862.5	789.1	708.7	631.3	562.8	507.2	463.5	426.8	395.0	382.1	369.2
135°	821.8	757.3	686.9	620.4	561.8	513.2	473.5	439.7	408.9	395.5	382.1
137.5°	783.1	725.6	666.0	610.4	559.8	517.1	481.4	448.6	418.9	406.4	394.0
140°	746.4	698.8	648.1	601.5	558.8	521.1	487.3	457.6	428.8	416.4	404.0
142.5°	712.7	673.0	631.3	593.6	556.8	524.1	493.3	464.5	436.7	425.3	413.9
145°	682.9	651.1	618.4	586.6	554.8	525.1	497.3	470.5	444.7	433.2	421.8
147.5°	661.0	634.2	607.4	579.7	551.9	525.1	500.3	475.4	451.6	441.7	431.8
150°	639.2	618.4	595.5	572.7	547.9	525.1	501.2	480.4	457.6	448.6	439.7
152.5°	621.3	603.5	584.6	564.8	542.9	522.1	503.2	483.4	464.5	456.0	447.6
155°	604.5	589.6	573.7	556.8	537.0	520.1	503.2	487.3	470.5	463.6	456.6
157.5°	587.6	575.7	561.8	547.9	532.0	517.1	504.2	489.3	475.4	470.0	464.5
160°	572.7	562.8	551.9	539.0	526.1	515.1	504.2	492.3	480.4	475.4	470.5
162.5°	557.8	548.9	540.0	530.0	520.1	511.2	503.2	493.3	483.4	479.4	475.4
165°	542.9	536.0	530.0	522.1	514.1	507.2	501.2	494.3	486.4	482.9	479.4
167.5°	530.0	526.1	521.1	514.1	508.2	503.2	500.3	494.3	488.3	485.8	483.4
170°	519.1	515.1	512.2	507.2	502.2	499.3	497.3	493.3	488.3	487.4	486.4
172.5°	509.2	506.2	504.2	500.3	497.3	496.3	496.3	493.3	489.3	488.8	488.3
175°	500.3	498.3	497.3	495.3	493.3	493.3	494.3	492.3	490.3	489.8	489.3
177.5°	494.3	493.3	492.3	491.3	490.3	491.3	493.3	491.3	490.3	490.3	490.3
180°	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3

TEST NUMBER: P1011039

CATALOG NUMBER: S123DIP-B1000D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1402.2	1402.2	1402.2	1402.2
2.5°	1372.3	1376.4	1390.0	1406.3
5°	1345.1	1356.0	1375.0	1400.8
7.5°	1315.2	1331.5	1358.7	1391.3
10°	1281.3	1304.4	1338.3	1379.1
12.5°	1244.6	1274.5	1317.9	1360.1
15°	1221.5	1251.4	1290.8	1337.0
17.5°	1176.6	1212.0	1252.7	1317.9
20°	1130.4	1169.8	1222.8	1288.0
22.5°	1095.1	1137.2	1187.5	1256.8
25°	1053.0	1096.5	1150.8	1222.8
27.5°	1008.2	1051.6	1112.8	1188.9
30°	974.2	1016.3	1074.7	1156.3
32.5°	933.4	974.2	1035.3	1120.9
35°	887.2	933.4	991.9	1078.8
37.5°	851.9	894.0	955.2	1038.0
40°	813.9	850.5	910.3	991.9
42.5°	773.1	813.9	865.5	947.0
45°	735.1	764.9	817.9	895.4
47.5°	694.3	728.3	769.0	828.8
50°	650.8	679.4	724.2	764.9
52.5°	608.7	631.8	669.8	701.1
55°	563.9	587.0	615.5	634.5
57.5°	521.7	538.0	557.1	569.3
60°	470.1	486.4	498.6	510.9
62.5°	423.9	436.1	442.9	449.7
65°	376.4	383.2	387.2	392.7
67.5°	324.7	331.5	332.9	341.0
70°	277.2	278.5	281.3	285.3
72.5°	232.3	235.1	233.7	236.4
75°	186.1	188.9	186.1	188.9
77.5°	141.3	144.0	144.0	148.1
80°	101.9	103.3	104.6	104.6
82.5°	66.6	70.7	67.9	69.3
85°	38.0	39.4	39.4	40.8
87.5°	17.7	19.0	17.7	20.4
90°	8.9	6.0	4.0	2.0
92.5°	40.7	31.8	21.8	14.9
95°	64.5	47.6	36.7	33.7
97.5°	78.4	63.5	54.6	53.6
100°	95.3	81.4	74.4	73.4
102.5°	115.1	102.2	96.3	94.3
105°	136.0	124.1	118.1	115.1
107.5°	157.8	145.9	140.0	137.0
110°	179.7	168.7	163.8	160.8

TEST NUMBER: P1011039

CATALOG NUMBER: S123DIP-B1000D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	201.5	190.6	185.6	182.6
115°	223.3	213.4	207.4	203.5
117.5°	243.2	234.2	229.3	224.3
120°	264.0	254.1	249.1	246.2
122.5°	283.9	273.0	268.0	265.0
125°	301.7	290.8	284.9	282.9
127.5°	317.6	306.7	299.8	296.8
130°	333.5	321.6	312.7	309.7
132.5°	348.4	333.5	323.6	319.6
135°	361.3	346.4	335.5	331.5
137.5°	373.2	357.3	346.4	342.4
140°	384.1	368.2	358.3	353.4
142.5°	394.0	380.2	369.2	365.3
145°	405.0	390.1	381.1	378.2
147.5°	414.9	402.0	393.1	391.1
150°	425.8	412.9	405.0	404.0
152.5°	435.7	424.8	416.9	416.9
155°	445.7	435.7	429.8	429.8
157.5°	454.6	445.7	440.7	439.7
160°	463.5	455.6	451.6	451.6
162.5°	469.5	463.5	460.5	460.5
165°	475.4	470.5	468.5	469.5
167.5°	480.4	476.4	475.4	476.4
170°	484.4	481.4	480.4	482.4
172.5°	487.3	485.4	485.4	486.4
175°	489.3	487.3	488.3	489.3
177.5°	490.3	489.3	490.3	491.3
180°	490.3	490.3	490.3	490.3

(END OF REPORT)