

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011048

Luminaire Tested: S123DIP-B1000D1025UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011048
REPORT IS A COMBINATION OF REPORTS P989063 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D1025UB40-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7844.0 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011048

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1011048

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	87	91	88	85	82	75	73	71	64	62	60	53	52	51
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	37	34	32
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	34	31	28
6	64	52	44	38	59	49	41	36	42	37	32	36	32	29	31	27	25
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20
9	51	39	32	26	47	37	30	25	32	27	23	28	23	20	24	20	18
10	48	36	29	24	44	34	27	23	30	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14944	14944	14944	14944
5°	14953	17217	14997	12850
10°	14858	20835	14872	11221
15°	14653	24709	14772	10100
20°	14476	28448	14507	9294
25°	14213	29165	14245	8874
30°	14026	24096	14026	8598
35°	13794	16115	13707	8355
40°	13515	11633	13348	7982
45°	13166	9215	12785	7518
50°	12316	7826	11879	7063
55°	11383	6877	10921	6555
60°	10437	5987	9882	6022
65°	9399	5127	8942	5311
70°	8319	4255	7766	4477
75°	7113	3210	6653	3457
80°	5624	2143	5185	2270
85°	3881	984	3103	895

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 24100 cd/sqm

TEST NUMBER: P1011048

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.5	1.7
10°-20°	438.5	5.6
20°-30°	737.9	9.4
30°-40°	833.9	10.6
40°-50°	746.8	9.5
50°-60°	602.9	7.7
60°-70°	420.1	5.4
70°-80°	220.5	2.8
80°-90°	55.5	0.7
90°-100°	263.4	3.4
100°-110°	771.2	9.8
110°-120°	753.1	9.6
120°-130°	599.7	7.6
130°-140°	473.2	6.0
140°-150°	353.0	4.5
150°-160°	246.1	3.1
160°-170°	144.6	1.8
170°-180°	47.0	0.6
0°-30°	1312.9	16.7
0°-40°	2146.8	27.4
0°-60°	3496.5	44.6
0°-90°	4192.7	53.5
90°-120°	1787.6	22.8
90°-150°	3213.6	41.0
90°-180°	3651.0	46.5
0°-180°	7844.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1388	1388	1388	1388	1388	
5°	1387	1649	1391	1231	1387	132
15°	1324	2455	1334	1004	1324	374
25°	1211	2914	1213	886	1211	559
35°	1068	1570	1061	814	1068	668
45°	886	848	861	691	886	678
55°	628	576	603	549	628	562
65°	389	374	370	387	389	387
75°	187	192	175	207	187	201
85°	40	44	32	40	40	46
90°	2	28	2	28	2	5
95°	33	114	33	114	33	35
105°	114	1250	114	1250	114	121
115°	201	1520	201	1520	201	199
125°	280	1199	280	1199	280	249
135°	328	972	328	972	328	254
145°	374	760	374	760	374	235
155°	426	630	426	630	426	196
165°	465	549	465	549	465	131
175°	484	494	484	494	484	46
180°	485	485	485	485	485	

TEST NUMBER: P1011048

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1392.3	1403.1	1408.4	1416.5	1424.6	1436.7	1440.7	1447.5	1444.8	1450.1	1452.8
5°	1386.9	1405.8	1421.9	1442.1	1460.9	1474.4	1487.8	1509.3	1525.5	1528.2	1540.3
7.5°	1377.5	1404.4	1432.7	1460.9	1497.2	1518.7	1543.0	1572.6	1596.8	1635.8	1650.6
10°	1365.4	1403.1	1443.4	1482.4	1532.2	1565.8	1595.4	1645.2	1695.0	1735.3	1773.0
12.5°	1346.6	1393.6	1446.1	1504.0	1568.5	1607.5	1647.9	1713.8	1789.1	1851.0	1891.4
15°	1323.7	1382.9	1450.1	1512.0	1583.3	1656.0	1699.0	1773.0	1880.6	1938.5	2042.0
17.5°	1304.9	1365.4	1432.7	1529.5	1626.4	1699.0	1729.9	1865.8	1939.8	2036.7	2153.7
20°	1275.3	1351.9	1438.0	1534.9	1660.0	1704.4	1767.6	1904.8	1996.3	2122.8	2266.7
22.5°	1244.3	1326.4	1430.0	1530.9	1670.8	1717.8	1803.9	1912.9	2058.2	2183.3	2342.0
25°	1210.7	1299.5	1404.4	1524.1	1661.3	1729.9	1810.7	1945.2	2102.6	2260.0	2406.6
27.5°	1177.1	1273.9	1382.9	1502.6	1635.8	1716.5	1797.2	1937.1	2138.9	2309.7	2496.7
30°	1144.8	1241.6	1350.6	1473.0	1612.9	1690.9	1767.6	1942.5	2167.1	2359.5	2547.8
32.5°	1109.8	1209.3	1323.7	1425.9	1567.2	1650.6	1736.7	1942.5	2184.6	2389.1	2561.3
35°	1068.1	1170.3	1268.5	1370.8	1510.7	1603.5	1700.4	1929.0	2200.8	2398.5	2504.8
37.5°	1027.7	1117.9	1202.6	1302.2	1448.8	1548.3	1660.0	1912.9	2192.7	2358.2	2387.8
40°	982.0	1072.1	1140.7	1233.6	1388.3	1504.0	1616.9	1891.4	2157.7	2262.7	2176.6
42.5°	937.6	1008.9	1068.1	1158.2	1326.4	1439.4	1561.8	1852.4	2089.1	2110.6	1916.9
45°	886.5	937.6	990.1	1092.3	1259.1	1374.8	1510.7	1795.9	1978.8	1916.9	1672.1
47.5°	820.6	866.3	924.2	1018.3	1187.8	1307.5	1436.7	1723.2	1818.7	1689.6	1421.9
50°	757.4	796.4	850.2	941.7	1112.5	1229.5	1366.7	1608.9	1656.0	1452.8	1225.5
52.5°	694.1	723.7	776.2	867.7	1038.5	1151.5	1276.6	1491.8	1464.9	1247.0	1045.2
55°	628.2	653.8	703.5	793.7	952.4	1060.0	1179.8	1347.9	1278.0	1070.8	909.4
57.5°	563.6	590.5	641.7	717.0	866.3	971.2	1066.8	1198.6	1093.7	928.2	785.6
60°	505.8	528.7	567.7	641.7	777.5	862.3	949.7	1039.9	952.4	792.3	683.4
62.5°	445.3	466.8	503.1	570.4	687.4	762.7	832.7	906.7	809.8	692.8	595.9
65°	388.8	406.3	439.9	501.8	597.3	659.2	715.7	766.8	688.8	581.1	508.5
67.5°	337.6	352.4	380.7	435.8	516.6	561.0	606.7	649.7	583.8	497.7	435.8
70°	282.5	294.6	320.2	360.5	425.1	470.8	504.5	536.7	477.6	408.9	367.2
72.5°	234.1	246.2	262.3	304.0	348.4	376.7	413.0	430.5	396.8	340.3	298.6
75°	187.0	196.4	211.2	238.1	279.8	298.6	321.5	335.0	304.0	266.4	240.8
77.5°	146.6	150.7	161.4	180.3	208.5	230.0	247.5	255.6	234.1	209.9	188.3
80°	103.6	109.0	117.0	133.2	154.7	161.4	172.2	181.6	168.2	146.6	133.2
82.5°	68.6	75.3	79.4	86.1	99.5	107.6	110.3	118.4	106.3	98.2	92.8
85°	40.4	43.0	44.4	48.4	55.2	59.2	63.2	64.6	61.9	60.5	55.2
87.5°	20.2	20.2	20.2	22.9	24.2	26.9	28.2	28.2	28.2	26.9	25.6
90°	2.0	3.9	5.9	8.8	10.8	11.8	12.8	15.7	18.7	21.6	24.6
92.5°	14.7	21.6	31.4	40.3	50.1	59.0	67.8	99.2	151.3	202.4	182.8
95°	33.4	36.4	47.2	63.9	89.4	108.6	127.7	211.3	357.7	518.8	582.7
97.5°	53.1	54.0	62.9	77.6	103.2	124.3	145.4	228.0	398.0	669.2	896.1
100°	72.7	73.7	80.6	94.3	117.9	137.0	156.2	225.0	370.4	628.9	930.5
102.5°	93.3	95.3	101.2	114.0	134.6	151.8	169.0	228.9	346.9	569.9	866.7
105°	114.0	116.9	122.8	134.6	153.3	168.5	183.7	236.8	338.0	523.7	790.0
107.5°	135.6	138.5	144.4	156.2	173.9	188.2	202.4	249.6	336.1	490.3	722.2
110°	159.2	162.1	167.0	177.9	194.6	208.4	222.1	266.3	341.0	472.6	666.2

TEST NUMBER: P1011048

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	180.8	183.7	188.7	199.5	216.2	229.4	242.7	283.0	350.8	462.8	628.9
115°	201.4	205.4	211.3	221.1	237.8	251.0	264.3	301.7	361.6	461.8	604.3
117.5°	222.1	227.0	231.9	240.7	259.4	271.7	284.0	321.3	375.4	462.8	587.6
120°	243.7	246.6	251.5	261.4	280.0	292.3	304.6	340.0	391.1	466.7	576.8
122.5°	262.4	265.3	270.2	281.0	298.7	312.0	325.2	359.6	405.8	473.6	569.9
125°	280.0	282.0	287.9	298.7	317.4	330.6	343.9	378.3	421.5	480.5	564.0
127.5°	293.8	296.7	303.6	314.4	335.1	348.4	361.6	395.0	434.3	488.4	561.1
130°	306.6	309.5	318.4	330.2	350.8	364.0	377.3	409.7	447.1	496.2	558.1
132.5°	316.4	320.3	330.2	344.9	365.5	378.3	391.1	422.5	458.9	502.1	557.1
135°	328.2	332.1	342.9	357.7	378.3	391.6	404.8	435.3	468.7	508.0	556.2
137.5°	339.0	342.9	353.7	369.5	390.1	402.4	414.7	444.1	476.6	511.9	554.2
140°	349.8	354.7	364.5	380.3	399.9	412.2	424.5	453.0	482.5	515.9	553.2
142.5°	361.6	365.5	376.3	390.1	409.7	421.0	432.4	459.9	488.4	518.8	551.2
145°	374.4	377.3	386.2	400.9	417.6	428.9	440.2	465.8	492.3	519.8	549.3
147.5°	387.1	389.1	398.0	410.7	427.4	437.2	447.1	470.7	495.2	519.8	546.3
150°	399.9	400.9	408.8	421.5	435.3	444.2	453.0	475.6	496.2	519.8	542.4
152.5°	412.7	412.7	420.6	431.4	443.2	451.6	459.9	478.5	498.2	516.9	537.5
155°	425.5	425.5	431.4	441.2	452.0	458.9	465.8	482.5	498.2	514.9	531.6
157.5°	435.3	436.3	441.2	450.0	459.9	465.3	470.7	484.4	499.2	511.9	526.7
160°	447.1	447.1	451.0	458.9	465.8	470.7	475.6	487.4	499.2	510.0	520.8
162.5°	455.9	455.9	458.9	464.8	470.7	474.6	478.5	488.4	498.2	506.0	514.9
165°	464.8	463.8	465.8	470.7	474.6	478.0	481.5	489.3	496.2	502.1	509.0
167.5°	471.7	470.7	471.7	475.6	478.5	481.0	483.4	489.3	495.2	498.2	503.1
170°	477.6	475.6	476.6	479.5	481.5	482.4	483.4	488.4	492.3	494.3	497.2
172.5°	481.5	480.5	480.5	482.5	483.4	483.9	484.4	488.4	491.3	491.3	492.3
175°	484.4	483.4	482.5	484.4	484.4	484.9	485.4	487.4	489.3	488.4	488.4
177.5°	486.4	485.4	484.4	485.4	485.4	485.4	485.4	486.4	488.4	486.4	485.4
180°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4

TEST NUMBER: P1011048

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1462.2	1464.9	1474.4	1481.1	1494.5	1493.2	1493.2	1491.8	1487.8	1494.5	1498.6
5°	1564.5	1587.4	1590.0	1619.6	1621.0	1633.1	1641.2	1634.4	1650.6	1649.2	1637.1
7.5°	1690.9	1721.9	1736.7	1764.9	1797.2	1789.1	1820.1	1825.5	1822.8	1836.2	1845.6
10°	1829.5	1883.3	1921.0	1973.4	1986.9	1995.0	2015.1	2032.6	2067.6	2040.7	2058.2
12.5°	1988.2	2027.2	2077.0	2160.4	2202.1	2229.0	2238.4	2250.5	2274.8	2260.0	2261.3
15°	2121.4	2173.9	2258.6	2362.2	2374.3	2407.9	2399.9	2472.5	2507.5	2455.0	2484.6
17.5°	2260.0	2329.9	2430.8	2520.9	2572.1	2594.9	2616.4	2686.4	2683.7	2675.6	2682.4
20°	2348.7	2463.1	2588.2	2707.9	2722.7	2740.2	2798.0	2827.6	2822.3	2845.1	2859.9
22.5°	2473.9	2594.9	2728.1	2807.5	2841.1	2861.3	2907.0	2925.8	2933.9	2939.3	2929.9
25°	2578.8	2707.9	2806.1	2876.1	2896.2	2907.0	2921.8	2927.2	2923.2	2913.7	2921.8
27.5°	2650.1	2753.7	2820.9	2853.2	2842.4	2825.0	2796.7	2777.9	2736.2	2716.0	2740.2
30°	2679.7	2725.4	2745.6	2691.8	2638.0	2594.9	2541.1	2441.6	2363.5	2386.4	2355.5
32.5°	2632.6	2603.0	2506.1	2367.6	2325.9	2255.9	2103.9	1986.9	1990.9	1929.0	1954.6
35°	2494.0	2359.5	2176.6	1966.7	1911.6	1873.9	1707.1	1681.5	1627.7	1569.9	1586.0
37.5°	2249.2	2052.8	1830.8	1676.1	1594.1	1512.0	1417.9	1361.4	1329.1	1304.9	1323.7
40°	1950.6	1711.1	1528.2	1389.6	1319.7	1267.2	1202.6	1146.1	1109.8	1105.8	1112.5
42.5°	1657.3	1455.5	1287.4	1155.5	1132.7	1070.8	1029.1	984.7	973.9	956.4	965.9
45°	1403.1	1238.9	1100.4	992.8	965.9	949.7	898.6	870.4	858.2	847.5	863.6
47.5°	1218.8	1046.6	945.7	881.1	854.2	827.3	799.1	780.2	770.8	772.2	770.8
50°	1041.2	914.7	826.0	776.2	760.0	741.2	718.3	706.2	702.2	690.1	699.5
52.5°	895.9	804.4	742.6	695.5	683.4	669.9	651.1	644.4	634.9	632.3	632.3
55°	778.9	707.6	657.8	626.9	612.1	601.3	590.5	582.5	575.8	575.8	575.8
57.5°	687.4	625.5	589.2	562.3	556.9	546.2	534.1	534.1	524.6	523.3	527.3
60°	609.4	554.2	526.0	503.1	495.0	492.3	480.2	480.2	477.6	470.8	476.2
62.5°	530.0	489.7	465.4	448.0	439.9	439.9	430.5	423.7	423.7	425.1	422.4
65°	457.4	427.8	406.3	392.8	388.8	383.4	382.0	376.7	372.6	374.0	372.6
67.5°	392.8	369.9	355.1	344.4	337.6	335.0	330.9	330.9	328.2	329.6	322.9
70°	335.0	312.1	300.0	289.2	286.5	286.5	281.2	282.5	279.8	283.8	281.2
72.5°	275.8	258.3	248.9	244.8	242.1	240.8	238.1	235.4	234.1	236.8	235.4
75°	223.3	208.5	201.8	199.1	196.4	196.4	195.1	193.7	192.4	192.4	192.4
77.5°	173.5	164.1	156.0	158.7	154.7	156.0	152.0	152.0	153.4	152.0	152.0
80°	127.8	121.1	121.1	118.4	113.0	115.7	115.7	111.7	110.3	113.0	109.0
82.5°	84.7	83.4	80.7	79.4	76.7	78.0	76.7	75.3	74.0	76.7	74.0
85°	49.8	49.8	48.4	45.7	48.4	47.1	45.7	45.7	44.4	44.4	44.4
87.5°	25.6	22.9	22.9	21.5	22.9	20.2	21.5	20.2	18.8	20.2	18.8
90°	23.6	24.6	25.5	26.5	27.5	28.5	27.5	28.5	29.5	28.5	29.5
92.5°	136.6	97.3	75.7	65.8	62.4	59.0	57.0	53.1	54.0	52.1	54.0
95°	472.6	353.7	239.8	187.7	170.0	152.3	133.6	124.8	117.9	114.0	117.9
97.5°	926.6	812.6	613.2	483.4	427.4	371.4	305.6	268.3	244.7	233.9	244.7
100°	1124.1	1158.5	1078.9	963.9	894.2	824.4	725.2	653.4	615.1	616.1	615.1
102.5°	1133.9	1273.5	1290.2	1235.1	1197.3	1159.5	1087.8	1034.7	1004.2	975.7	1004.2
105°	1072.0	1277.4	1375.7	1394.3	1381.6	1368.8	1323.6	1286.2	1254.8	1249.9	1254.8
107.5°	983.6	1218.4	1372.7	1449.4	1462.6	1475.9	1470.0	1452.3	1439.5	1428.7	1439.5
110°	901.1	1126.1	1306.9	1430.7	1465.1	1499.5	1527.0	1534.8	1532.9	1530.9	1532.9

TEST NUMBER: P1011048

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	829.3	1034.7	1220.4	1362.9	1409.6	1456.2	1512.2	1540.7	1550.6	1551.5	1550.6
115°	774.3	956.1	1127.1	1271.5	1325.0	1378.6	1452.3	1495.5	1515.2	1520.1	1515.2
117.5°	737.9	895.2	1046.5	1179.1	1234.6	1290.2	1366.8	1415.0	1444.4	1451.3	1444.4
120°	710.4	849.0	981.6	1099.5	1149.2	1198.8	1276.4	1331.4	1355.0	1360.9	1355.0
122.5°	687.8	812.6	929.6	1036.7	1081.9	1127.1	1193.9	1242.0	1268.6	1276.4	1268.6
125°	669.2	781.2	888.3	982.6	1021.9	1061.2	1124.1	1167.3	1191.9	1198.8	1191.9
127.5°	651.5	752.7	850.0	936.4	972.8	1009.1	1066.1	1103.5	1126.1	1132.0	1126.1
130°	637.7	726.2	814.6	894.2	927.6	961.0	1013.1	1048.4	1069.1	1076.9	1069.1
132.5°	624.9	701.6	781.2	853.9	885.4	916.8	964.9	1000.3	1018.0	1022.9	1018.0
135°	614.1	680.0	749.7	813.6	841.6	869.6	917.8	947.2	964.9	971.8	964.9
137.5°	604.3	659.3	718.3	775.3	800.3	825.4	866.7	897.1	911.9	917.8	911.9
140°	595.5	641.6	691.8	738.9	760.0	781.2	818.5	846.0	861.8	860.8	861.8
142.5°	587.6	624.9	666.2	705.5	723.2	740.9	771.4	794.9	808.7	807.7	808.7
145°	580.7	612.2	644.6	676.0	690.2	704.5	729.1	749.7	757.6	759.6	757.6
147.5°	573.8	601.4	627.9	654.4	664.8	675.1	694.7	709.4	717.3	718.3	717.3
150°	567.0	589.6	612.2	632.8	642.2	651.5	666.2	677.0	682.9	682.9	682.9
152.5°	559.1	578.8	597.4	615.1	622.5	629.9	640.7	650.5	653.4	653.4	653.4
155°	551.2	568.0	583.7	598.4	604.3	610.2	619.0	626.9	628.9	629.9	628.9
157.5°	542.4	556.2	569.9	581.7	586.6	591.5	599.4	605.3	607.3	607.3	607.3
160°	533.6	546.3	557.1	567.0	570.4	573.8	580.7	586.6	586.6	585.6	586.6
162.5°	524.7	534.5	543.4	552.2	555.2	558.1	562.1	567.0	567.0	566.0	567.0
165°	516.9	524.7	530.6	537.5	540.0	542.4	546.3	550.3	549.3	549.3	549.3
167.5°	509.0	515.9	520.8	524.7	526.7	528.6	530.6	533.6	532.6	532.6	532.6
170°	502.1	507.0	510.0	513.9	514.9	515.9	516.9	518.8	517.8	517.8	517.8
172.5°	495.2	499.2	501.1	504.1	504.6	505.1	505.1	507.0	505.1	504.1	505.1
175°	490.3	492.3	493.3	495.2	495.2	495.2	495.2	496.2	495.2	494.3	495.2
177.5°	486.4	487.4	488.4	489.3	489.3	489.3	488.4	489.3	487.4	487.4	487.4
180°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4

TEST NUMBER: P1011048

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1487.8	1491.8	1481.1	1478.4	1478.4	1483.8	1479.7	1443.4	1450.1	1442.1	1439.4
5°	1651.9	1643.9	1633.1	1627.7	1621.0	1602.2	1600.8	1559.1	1551.0	1524.1	1512.0
7.5°	1832.2	1825.5	1793.2	1789.1	1786.4	1769.0	1724.6	1680.2	1647.9	1616.9	1587.4
10°	2038.0	2017.8	2003.0	1973.4	1958.6	1934.4	1876.6	1834.9	1779.7	1732.6	1670.8
12.5°	2285.5	2262.7	2212.9	2191.4	2172.5	2105.3	2047.4	2000.3	1892.7	1860.4	1783.8
15°	2467.1	2418.7	2413.3	2366.2	2363.5	2289.6	2179.2	2128.1	2044.7	1926.3	1847.0
17.5°	2663.5	2620.5	2586.9	2530.4	2522.3	2452.3	2371.6	2246.5	2155.0	2042.0	1941.1
20°	2807.5	2784.6	2726.8	2703.9	2656.8	2597.6	2514.2	2359.5	2247.9	2134.9	2011.1
22.5°	2921.8	2898.9	2853.2	2822.3	2795.4	2718.7	2619.1	2487.3	2333.9	2186.0	2058.2
25°	2920.5	2913.7	2894.9	2880.1	2859.9	2803.4	2720.0	2593.6	2422.7	2260.0	2082.4
27.5°	2755.0	2773.8	2806.1	2822.3	2818.2	2810.2	2763.1	2656.8	2503.4	2309.7	2110.6
30°	2410.6	2479.2	2539.8	2620.5	2644.7	2703.9	2730.8	2670.3	2547.8	2367.6	2147.0
32.5°	1999.0	2098.5	2230.4	2274.8	2351.4	2465.8	2593.6	2616.4	2539.8	2401.2	2169.8
35°	1639.8	1721.9	1824.1	1894.1	1962.7	2148.3	2309.7	2449.6	2475.2	2383.7	2164.5
37.5°	1357.3	1415.2	1505.3	1564.5	1627.7	1786.4	2012.4	2194.0	2321.8	2324.5	2149.7
40°	1152.9	1178.4	1256.4	1299.5	1360.0	1497.2	1699.0	1935.8	2122.8	2208.8	2110.6
42.5°	976.6	1010.3	1074.8	1107.1	1146.1	1265.8	1399.0	1623.7	1855.1	2039.3	2038.0
45°	871.7	895.9	925.5	952.4	996.8	1068.1	1220.1	1388.3	1610.2	1818.7	1900.8
47.5°	778.9	801.7	831.3	839.4	869.0	936.3	1029.1	1175.7	1382.9	1590.0	1744.7
50°	700.9	719.7	739.9	754.7	768.1	823.3	893.2	1017.0	1182.4	1382.9	1575.2
52.5°	640.3	653.8	671.3	679.3	691.4	731.8	785.6	877.1	1012.9	1195.9	1382.9
55°	583.8	593.2	604.0	617.5	622.8	652.4	694.1	772.2	873.0	1037.2	1214.7
57.5°	531.4	535.4	542.1	550.2	556.9	582.5	618.8	671.3	760.0	886.5	1054.6
60°	472.2	482.9	487.0	495.0	499.1	519.3	547.5	591.9	660.5	769.5	895.9
62.5°	422.4	429.1	435.8	439.9	449.3	456.0	478.9	519.3	575.8	656.5	770.8
65°	378.0	380.7	384.7	388.8	391.5	399.5	421.1	448.0	491.0	562.3	651.1
67.5°	326.9	329.6	335.0	336.3	339.0	349.8	361.9	384.7	421.1	474.9	547.5
70°	277.1	281.2	283.8	286.5	290.6	294.6	308.1	326.9	355.1	392.8	449.3
72.5°	234.1	238.1	238.1	240.8	239.4	244.8	258.3	271.7	290.6	321.5	371.3
75°	191.0	191.0	193.7	195.1	196.4	201.8	207.2	217.9	232.7	256.9	287.9
77.5°	150.7	149.3	152.0	152.0	152.0	156.0	161.4	166.8	176.2	193.7	217.9
80°	110.3	110.3	113.0	114.3	111.7	113.0	115.7	121.1	127.8	139.9	153.4
82.5°	72.6	78.0	76.7	78.0	76.7	79.4	80.7	82.1	84.7	90.1	99.5
85°	44.4	44.4	44.4	45.7	44.4	45.7	45.7	45.7	47.1	49.8	53.8
87.5°	18.8	18.8	18.8	20.2	18.8	18.8	20.2	18.8	20.2	20.2	21.5
90°	28.5	27.5	28.5	27.5	26.5	25.5	24.6	23.6	24.6	21.6	18.7
92.5°	53.1	57.0	59.0	62.4	65.8	75.7	97.3	136.6	182.8	202.4	151.3
95°	124.8	133.6	152.3	170.0	187.7	239.8	353.7	472.6	582.7	518.8	357.7
97.5°	268.3	305.6	371.4	427.4	483.4	613.2	812.6	926.6	896.1	669.2	398.0
100°	653.4	725.2	824.4	894.2	963.9	1078.9	1158.5	1124.1	930.5	628.9	370.4
102.5°	1034.7	1087.8	1159.5	1197.3	1235.1	1290.2	1273.5	1133.9	866.7	569.9	346.9
105°	1286.2	1323.6	1368.8	1381.6	1394.3	1375.7	1277.4	1072.0	790.0	523.7	338.0
107.5°	1452.3	1470.0	1475.9	1462.6	1449.4	1372.7	1218.4	983.6	722.2	490.3	336.1
110°	1534.8	1527.0	1499.5	1465.1	1430.7	1306.9	1126.1	901.1	666.2	472.6	341.0

TEST NUMBER: P1011048

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1540.7	1512.2	1456.2	1409.6	1362.9	1220.4	1034.7	829.3	628.9	462.8	350.8
115°	1495.5	1452.3	1378.6	1325.0	1271.5	1127.1	956.1	774.3	604.3	461.8	361.6
117.5°	1415.0	1366.8	1290.2	1234.6	1179.1	1046.5	895.2	737.9	587.6	462.8	375.4
120°	1331.4	1276.4	1198.8	1149.2	1099.5	981.6	849.0	710.4	576.8	466.7	391.1
122.5°	1242.0	1193.9	1127.1	1081.9	1036.7	929.6	812.6	687.8	569.9	473.6	405.8
125°	1167.3	1124.1	1061.2	1021.9	982.6	888.3	781.2	669.2	564.0	480.5	421.5
127.5°	1103.5	1066.1	1009.1	972.8	936.4	850.0	752.7	651.5	561.1	488.4	434.3
130°	1048.4	1013.1	961.0	927.6	894.2	814.6	726.2	637.7	558.1	496.2	447.1
132.5°	1000.3	964.9	916.8	885.4	853.9	781.2	701.6	624.9	557.1	502.1	458.9
135°	947.2	917.8	869.6	841.6	813.6	749.7	680.0	614.1	556.2	508.0	468.7
137.5°	897.1	866.7	825.4	800.3	775.3	718.3	659.3	604.3	554.2	511.9	476.6
140°	846.0	818.5	781.2	760.0	738.9	691.8	641.6	595.5	553.2	515.9	482.5
142.5°	794.9	771.4	740.9	723.2	705.5	666.2	624.9	587.6	551.2	518.8	488.4
145°	749.7	729.1	704.5	690.2	676.0	644.6	612.2	580.7	549.3	519.8	492.3
147.5°	709.4	694.7	675.1	664.8	654.4	627.9	601.4	573.8	546.3	519.8	495.2
150°	677.0	666.2	651.5	642.2	632.8	612.2	589.6	567.0	542.4	519.8	496.2
152.5°	650.5	640.7	629.9	622.5	615.1	597.4	578.8	559.1	537.5	516.9	498.2
155°	626.9	619.0	610.2	604.3	598.4	583.7	568.0	551.2	531.6	514.9	498.2
157.5°	605.3	599.4	591.5	586.6	581.7	569.9	556.2	542.4	526.7	511.9	499.2
160°	586.6	580.7	573.8	570.4	567.0	557.1	546.3	533.6	520.8	510.0	499.2
162.5°	567.0	562.1	558.1	555.2	552.2	543.4	534.5	524.7	514.9	506.0	498.2
165°	550.3	546.3	542.4	540.0	537.5	530.6	524.7	516.9	509.0	502.1	496.2
167.5°	533.6	530.6	528.6	526.7	524.7	520.8	515.9	509.0	503.1	498.2	495.2
170°	518.8	516.9	515.9	514.9	513.9	510.0	507.0	502.1	497.2	494.3	492.3
172.5°	507.0	505.1	505.1	504.6	504.1	501.1	499.2	495.2	492.3	491.3	491.3
175°	496.2	495.2	495.2	495.2	495.2	493.3	492.3	490.3	488.4	488.4	489.3
177.5°	489.3	488.4	489.3	489.3	489.3	488.4	487.4	486.4	485.4	486.4	488.4
180°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4

TEST NUMBER: P1011048

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1425.9	1421.9	1421.9	1419.2	1411.1	1396.3	1395.0	1397.7	1389.6	1381.5	1369.4
5°	1495.9	1470.3	1462.2	1454.2	1438.0	1411.1	1400.4	1391.0	1376.2	1358.7	1339.8
7.5°	1555.1	1518.7	1508.0	1493.2	1460.9	1423.2	1399.0	1378.8	1358.7	1334.5	1311.6
10°	1629.1	1576.6	1551.0	1529.5	1485.1	1432.7	1396.3	1366.7	1334.5	1304.9	1275.3
12.5°	1712.5	1627.7	1619.6	1567.2	1516.1	1438.0	1393.6	1350.6	1307.5	1271.2	1240.3
15°	1782.4	1689.6	1656.0	1621.0	1522.8	1425.9	1382.9	1334.5	1284.7	1245.7	1199.9
17.5°	1826.8	1750.1	1678.8	1631.7	1529.5	1443.4	1360.0	1304.9	1252.4	1198.6	1160.9
20°	1880.6	1769.0	1707.1	1643.9	1543.0	1430.0	1346.6	1278.0	1213.4	1165.0	1119.2
22.5°	1934.4	1783.8	1732.6	1664.0	1545.7	1416.5	1322.3	1253.7	1179.8	1131.3	1081.6
25°	1929.0	1805.3	1720.5	1662.7	1518.7	1404.4	1294.1	1213.4	1144.8	1082.9	1033.1
27.5°	1933.1	1781.1	1695.0	1627.7	1499.9	1386.9	1264.5	1179.8	1108.5	1043.9	991.4
30°	1934.4	1744.7	1669.4	1588.7	1464.9	1345.2	1230.9	1144.8	1069.4	999.5	952.4
32.5°	1930.4	1715.2	1621.0	1548.3	1409.8	1304.9	1191.9	1100.4	1023.7	959.1	914.7
35°	1921.0	1680.2	1571.2	1479.7	1353.3	1247.0	1155.5	1061.4	979.3	920.1	869.0
37.5°	1895.4	1642.5	1518.7	1428.6	1287.4	1179.8	1099.0	1021.0	941.7	871.7	828.7
40°	1876.6	1591.4	1466.3	1368.1	1216.1	1111.1	1043.9	969.9	891.9	828.7	787.0
42.5°	1833.5	1543.0	1412.5	1295.4	1146.1	1038.5	975.3	916.1	848.8	787.0	749.3
45°	1763.6	1490.5	1346.6	1228.2	1069.4	967.2	909.4	860.9	801.7	742.6	704.9
47.5°	1665.4	1415.2	1276.6	1158.2	994.1	890.5	832.7	796.4	749.3	699.5	667.2
50°	1559.1	1333.1	1205.3	1088.3	921.5	820.6	764.1	730.5	699.5	653.8	622.8
52.5°	1420.5	1245.7	1123.3	1011.6	843.5	746.6	696.8	672.6	640.3	608.0	581.1
55°	1286.0	1132.7	1031.8	925.5	766.8	676.6	628.2	602.7	583.8	556.9	535.4
57.5°	1130.0	1027.7	934.9	838.1	695.5	613.4	567.7	536.7	524.6	512.5	492.3
60°	986.0	908.0	832.7	752.0	621.5	547.5	503.1	478.9	466.8	458.7	445.3
62.5°	854.2	793.7	729.1	664.5	546.2	478.9	445.3	421.1	410.3	408.9	396.8
65°	727.8	684.7	632.3	569.0	476.2	417.0	384.7	369.9	357.8	357.8	348.4
67.5°	601.3	571.7	530.0	485.6	413.0	357.8	328.2	314.8	308.1	308.1	301.3
70°	500.4	480.2	442.6	403.6	340.3	298.6	275.8	263.7	259.6	261.0	255.6
72.5°	406.3	384.7	353.8	325.5	278.5	247.5	231.4	217.9	211.2	212.5	211.2
75°	314.8	304.0	277.1	255.6	217.9	196.4	181.6	174.9	169.5	170.8	168.2
77.5°	236.8	220.6	205.8	191.0	168.2	150.7	138.6	131.8	127.8	127.8	127.8
80°	161.4	158.7	146.6	138.6	119.7	106.3	96.9	95.5	91.5	91.5	91.5
82.5°	104.9	98.2	91.5	86.1	75.3	67.3	63.2	60.5	59.2	57.8	60.5
85°	57.8	53.8	51.1	45.7	41.7	37.7	33.6	32.3	30.9	32.3	30.9
87.5°	22.9	18.8	18.8	17.5	16.1	14.8	14.8	12.1	12.1	10.8	10.8
90°	15.7	12.8	11.8	10.8	8.8	5.9	3.9	2.0	3.9	5.9	8.8
92.5°	99.2	67.8	59.0	50.1	40.3	31.4	21.6	14.7	21.6	31.4	40.3
95°	211.3	127.7	108.6	89.4	63.9	47.2	36.4	33.4	36.4	47.2	63.9
97.5°	228.0	145.4	124.3	103.2	77.6	62.9	54.0	53.1	54.0	62.9	77.6
100°	225.0	156.2	137.0	117.9	94.3	80.6	73.7	72.7	73.7	80.6	94.3
102.5°	228.9	169.0	151.8	134.6	114.0	101.2	95.3	93.3	95.3	101.2	114.0
105°	236.8	183.7	168.5	153.3	134.6	122.8	116.9	114.0	116.9	122.8	134.6
107.5°	249.6	202.4	188.2	173.9	156.2	144.4	138.5	135.6	138.5	144.4	156.2
110°	266.3	222.1	208.4	194.6	177.9	167.0	162.1	159.2	162.1	167.0	177.9

TEST NUMBER: P1011048

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	283.0	242.7	229.4	216.2	199.5	188.7	183.7	180.8	183.7	188.7	199.5
115°	301.7	264.3	251.0	237.8	221.1	211.3	205.4	201.4	205.4	211.3	221.1
117.5°	321.3	284.0	271.7	259.4	240.7	231.9	227.0	222.1	227.0	231.9	240.7
120°	340.0	304.6	292.3	280.0	261.4	251.5	246.6	243.7	246.6	251.5	261.4
122.5°	359.6	325.2	312.0	298.7	281.0	270.2	265.3	262.4	265.3	270.2	281.0
125°	378.3	343.9	330.6	317.4	298.7	287.9	282.0	280.0	282.0	287.9	298.7
127.5°	395.0	361.6	348.4	335.1	314.4	303.6	296.7	293.8	296.7	303.6	314.4
130°	409.7	377.3	364.0	350.8	330.2	318.4	309.5	306.6	309.5	318.4	330.2
132.5°	422.5	391.1	378.3	365.5	344.9	330.2	320.3	316.4	320.3	330.2	344.9
135°	435.3	404.8	391.6	378.3	357.7	342.9	332.1	328.2	332.1	342.9	357.7
137.5°	444.1	414.7	402.4	390.1	369.5	353.7	342.9	339.0	342.9	353.7	369.5
140°	453.0	424.5	412.2	399.9	380.3	364.5	354.7	349.8	354.7	364.5	380.3
142.5°	459.9	432.4	421.0	409.7	390.1	376.3	365.5	361.6	365.5	376.3	390.1
145°	465.8	440.2	428.9	417.6	400.9	386.2	377.3	374.4	377.3	386.2	400.9
147.5°	470.7	447.1	437.2	427.4	410.7	398.0	389.1	387.1	389.1	398.0	410.7
150°	475.6	453.0	444.2	435.3	421.5	408.8	400.9	399.9	400.9	408.8	421.5
152.5°	478.5	459.9	451.6	443.2	431.4	420.6	412.7	412.7	412.7	420.6	431.4
155°	482.5	465.8	458.9	452.0	441.2	431.4	425.5	425.5	425.5	431.4	441.2
157.5°	484.4	470.7	465.3	459.9	450.0	441.2	436.3	435.3	436.3	441.2	450.0
160°	487.4	475.6	470.7	465.8	458.9	451.0	447.1	447.1	447.1	451.0	458.9
162.5°	488.4	478.5	474.6	470.7	464.8	458.9	455.9	455.9	455.9	458.9	464.8
165°	489.3	481.5	478.0	474.6	470.7	465.8	463.8	464.8	463.8	465.8	470.7
167.5°	489.3	483.4	481.0	478.5	475.6	471.7	470.7	471.7	470.7	471.7	475.6
170°	488.4	483.4	482.4	481.5	479.5	476.6	475.6	477.6	475.6	476.6	479.5
172.5°	488.4	484.4	483.9	483.4	482.5	480.5	480.5	481.5	480.5	480.5	482.5
175°	487.4	485.4	484.9	484.4	484.4	482.5	483.4	484.4	483.4	482.5	484.4
177.5°	486.4	485.4	485.4	485.4	485.4	484.4	485.4	486.4	485.4	484.4	485.4
180°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4

TEST NUMBER: P1011048

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1366.7	1365.4	1368.1	1360.0	1346.6	1339.8	1321.0	1317.0	1315.6	1317.0	1318.3
5°	1329.1	1327.7	1323.7	1310.2	1294.1	1282.0	1259.1	1257.8	1249.7	1241.6	1245.7
7.5°	1292.8	1287.4	1279.3	1261.8	1240.3	1226.8	1208.0	1194.6	1183.8	1177.1	1171.7
10°	1256.4	1248.4	1240.3	1217.4	1190.5	1170.3	1147.5	1136.7	1124.6	1119.2	1113.8
12.5°	1209.3	1201.3	1186.5	1159.6	1143.4	1117.9	1095.0	1084.2	1077.5	1066.8	1060.0
15°	1171.7	1155.5	1147.5	1119.2	1085.6	1082.9	1041.2	1038.5	1025.1	1025.1	1014.3
17.5°	1128.6	1116.5	1101.7	1073.5	1049.3	1025.1	1003.5	995.5	983.4	980.7	975.3
20°	1086.9	1070.8	1065.4	1037.2	1011.6	982.0	959.1	951.1	945.7	940.3	944.3
22.5°	1043.9	1030.4	1017.0	991.4	972.6	943.0	929.5	921.5	913.4	910.7	912.1
25°	1002.2	990.1	976.6	951.1	930.9	906.7	894.6	890.5	886.5	886.5	885.2
27.5°	961.8	949.7	937.6	914.7	894.6	877.1	867.7	863.6	859.6	862.3	865.0
30°	920.1	909.4	898.6	878.4	862.3	846.1	840.8	838.1	836.7	843.5	843.5
32.5°	882.5	873.0	865.0	846.1	830.0	816.5	812.5	813.9	815.2	819.2	821.9
35°	843.5	836.7	828.7	812.5	799.1	787.0	788.3	788.3	791.0	797.7	803.1
37.5°	808.5	799.1	792.3	778.9	768.1	757.4	761.4	765.4	768.1	776.2	778.9
40°	766.8	762.7	757.4	743.9	734.5	733.1	734.5	737.2	742.6	746.6	750.6
42.5°	733.1	727.8	721.0	710.3	702.2	703.5	704.9	707.6	710.3	717.0	721.0
45°	695.5	691.4	686.1	676.6	669.9	671.3	672.6	672.6	675.3	683.4	686.1
47.5°	653.8	655.1	648.4	639.0	634.9	634.9	634.9	637.6	644.4	647.0	648.4
50°	613.4	610.7	609.4	600.0	597.3	595.9	597.3	598.6	608.0	606.7	610.7
52.5°	570.4	570.4	569.0	563.6	559.6	559.6	556.9	563.6	566.3	569.0	573.1
55°	528.7	524.6	523.3	520.6	515.2	513.9	516.6	524.6	527.3	530.0	534.1
57.5°	482.9	482.9	480.2	476.2	476.2	476.2	476.2	481.6	485.6	488.3	496.4
60°	441.2	435.8	431.8	431.8	431.8	430.5	438.5	438.5	446.6	448.0	450.6
62.5°	391.5	388.8	386.1	387.4	386.1	388.8	391.5	396.8	398.2	402.2	406.3
65°	344.4	344.4	341.7	349.8	344.4	344.4	351.1	351.1	353.8	357.8	363.2
67.5°	298.6	300.0	297.3	297.3	300.0	301.3	302.7	308.1	309.4	314.8	321.5
70°	251.6	254.2	255.6	252.9	255.6	258.3	261.0	262.3	267.7	270.4	274.4
72.5°	209.9	212.5	208.5	209.9	211.2	213.9	215.2	217.9	220.6	228.7	231.4
75°	168.2	166.8	165.5	170.8	168.2	173.5	174.9	174.9	177.6	184.3	187.0
77.5°	129.1	129.1	130.5	127.8	131.8	130.5	131.8	135.9	139.9	139.9	150.7
80°	90.1	92.8	92.8	92.8	94.2	95.5	92.8	99.5	100.9	100.9	104.9
82.5°	57.8	59.2	57.8	60.5	60.5	63.2	61.9	63.2	65.9	68.6	70.0
85°	30.9	30.9	33.6	33.6	32.3	33.6	32.3	33.6	36.3	36.3	37.7
87.5°	10.8	10.8	10.8	10.8	12.1	10.8	12.1	12.1	10.8	10.8	14.8
90°	10.8	11.8	12.8	15.7	18.7	21.6	24.6	23.6	24.6	25.5	26.5
92.5°	50.1	59.0	67.8	99.2	151.3	202.4	182.8	136.6	97.3	75.7	65.8
95°	89.4	108.6	127.7	211.3	357.7	518.8	582.7	472.6	353.7	239.8	187.7
97.5°	103.2	124.3	145.4	228.0	398.0	669.2	896.1	926.6	812.6	613.2	483.4
100°	117.9	137.0	156.2	225.0	370.4	628.9	930.5	1124.1	1158.5	1078.9	963.9
102.5°	134.6	151.8	169.0	228.9	346.9	569.9	866.7	1133.9	1273.5	1290.2	1235.1
105°	153.3	168.5	183.7	236.8	338.0	523.7	790.0	1072.0	1277.4	1375.7	1394.3
107.5°	173.9	188.2	202.4	249.6	336.1	490.3	722.2	983.6	1218.4	1372.7	1449.4
110°	194.6	208.4	222.1	266.3	341.0	472.6	666.2	901.1	1126.1	1306.9	1430.7

TEST NUMBER: P1011048

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	216.2	229.4	242.7	283.0	350.8	462.8	628.9	829.3	1034.7	1220.4	1362.9
115°	237.8	251.0	264.3	301.7	361.6	461.8	604.3	774.3	956.1	1127.1	1271.5
117.5°	259.4	271.7	284.0	321.3	375.4	462.8	587.6	737.9	895.2	1046.5	1179.1
120°	280.0	292.3	304.6	340.0	391.1	466.7	576.8	710.4	849.0	981.6	1099.5
122.5°	298.7	312.0	325.2	359.6	405.8	473.6	569.9	687.8	812.6	929.6	1036.7
125°	317.4	330.6	343.9	378.3	421.5	480.5	564.0	669.2	781.2	888.3	982.6
127.5°	335.1	348.4	361.6	395.0	434.3	488.4	561.1	651.5	752.7	850.0	936.4
130°	350.8	364.0	377.3	409.7	447.1	496.2	558.1	637.7	726.2	814.6	894.2
132.5°	365.5	378.3	391.1	422.5	458.9	502.1	557.1	624.9	701.6	781.2	853.9
135°	378.3	391.6	404.8	435.3	468.7	508.0	556.2	614.1	680.0	749.7	813.6
137.5°	390.1	402.4	414.7	444.1	476.6	511.9	554.2	604.3	659.3	718.3	775.3
140°	399.9	412.2	424.5	453.0	482.5	515.9	553.2	595.5	641.6	691.8	738.9
142.5°	409.7	421.0	432.4	459.9	488.4	518.8	551.2	587.6	624.9	666.2	705.5
145°	417.6	428.9	440.2	465.8	492.3	519.8	549.3	580.7	612.2	644.6	676.0
147.5°	427.4	437.2	447.1	470.7	495.2	519.8	546.3	573.8	601.4	627.9	654.4
150°	435.3	444.2	453.0	475.6	496.2	519.8	542.4	567.0	589.6	612.2	632.8
152.5°	443.2	451.6	459.9	478.5	498.2	516.9	537.5	559.1	578.8	597.4	615.1
155°	452.0	458.9	465.8	482.5	498.2	514.9	531.6	551.2	568.0	583.7	598.4
157.5°	459.9	465.3	470.7	484.4	499.2	511.9	526.7	542.4	556.2	569.9	581.7
160°	465.8	470.7	475.6	487.4	499.2	510.0	520.8	533.6	546.3	557.1	567.0
162.5°	470.7	474.6	478.5	488.4	498.2	506.0	514.9	524.7	534.5	543.4	552.2
165°	474.6	478.0	481.5	489.3	496.2	502.1	509.0	516.9	524.7	530.6	537.5
167.5°	478.5	481.0	483.4	489.3	495.2	498.2	503.1	509.0	515.9	520.8	524.7
170°	481.5	482.4	483.4	488.4	492.3	494.3	497.2	502.1	507.0	510.0	513.9
172.5°	483.4	483.9	484.4	488.4	491.3	491.3	492.3	495.2	499.2	501.1	504.1
175°	484.4	484.9	485.4	487.4	489.3	488.4	488.4	490.3	492.3	493.3	495.2
177.5°	485.4	485.4	485.4	486.4	488.4	486.4	485.4	486.4	487.4	488.4	489.3
180°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4

TEST NUMBER: P1011048

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1317.0	1318.3	1312.9	1308.9	1319.7	1312.9	1312.9	1314.3	1311.6	1315.6	1314.3
5°	1243.0	1244.3	1234.9	1237.6	1232.2	1230.9	1229.5	1237.6	1236.3	1234.9	1237.6
7.5°	1170.3	1170.3	1166.3	1163.6	1163.6	1159.6	1165.0	1163.6	1166.3	1166.3	1170.3
10°	1109.8	1112.5	1105.8	1099.0	1097.7	1099.0	1099.0	1100.4	1101.7	1111.1	1109.8
12.5°	1060.0	1056.0	1054.6	1050.6	1043.9	1041.2	1038.5	1053.3	1049.3	1049.3	1049.3
15°	1004.9	1014.3	1012.9	1000.8	998.2	1003.5	1000.8	1000.8	1014.3	1012.9	1011.6
17.5°	975.3	972.6	969.9	963.2	964.5	963.2	964.5	964.5	972.6	972.6	972.6
20°	941.7	936.3	936.3	933.6	933.6	929.5	934.9	936.3	941.7	941.7	943.0
22.5°	912.1	908.0	908.0	906.7	909.4	904.0	909.4	910.7	910.7	914.7	914.7
25°	886.5	883.8	883.8	886.5	886.5	886.5	886.5	891.9	887.8	889.2	887.8
27.5°	863.6	865.0	866.3	867.7	866.3	867.7	869.0	871.7	873.0	871.7	869.0
30°	842.1	846.1	847.5	847.5	850.2	851.5	852.9	852.9	854.2	850.2	852.9
32.5°	826.0	826.0	828.7	830.0	832.7	834.0	834.0	836.7	835.4	831.3	832.7
35°	803.1	803.1	808.5	811.2	815.2	813.9	815.2	815.2	816.5	813.9	809.8
37.5°	780.2	782.9	782.9	788.3	789.6	791.0	789.6	792.3	791.0	788.3	787.0
40°	753.3	752.0	753.3	757.4	758.7	758.7	758.7	761.4	761.4	761.4	760.0
42.5°	719.7	723.7	722.4	726.4	725.1	725.1	727.8	730.5	731.8	727.8	729.1
45°	687.4	687.4	690.1	690.1	691.4	691.4	696.8	694.1	696.8	694.1	695.5
47.5°	652.4	653.8	653.8	655.1	657.8	660.5	657.8	659.2	659.2	660.5	657.8
50°	613.4	613.4	616.1	620.1	625.5	622.8	621.5	626.9	622.8	622.8	620.1
52.5°	573.1	577.1	578.4	582.5	586.5	587.9	589.2	586.5	587.9	583.8	585.2
55°	534.1	535.4	540.8	544.8	548.8	548.8	547.5	548.8	550.2	544.8	544.8
57.5°	495.0	499.1	504.5	504.5	509.8	509.8	508.5	508.5	509.8	505.8	504.5
60°	453.3	457.4	464.1	464.1	472.2	473.5	470.8	468.1	468.1	464.1	465.4
62.5°	408.9	413.0	417.0	423.7	429.1	426.4	431.8	426.4	427.8	419.7	419.7
65°	369.9	371.3	378.0	384.7	384.7	387.4	384.7	386.1	382.0	382.0	376.7
67.5°	324.2	324.2	330.9	337.6	344.4	344.4	344.4	340.3	340.3	336.3	336.3
70°	283.8	282.5	289.2	293.3	297.3	298.6	295.9	294.6	291.9	287.9	286.5
72.5°	234.1	236.8	243.5	246.2	252.9	251.6	258.3	250.2	250.2	243.5	242.1
75°	189.7	192.4	199.1	203.1	207.2	207.2	211.2	207.2	201.8	199.1	197.7
77.5°	150.7	149.3	154.7	161.4	162.8	161.4	164.1	162.8	157.4	157.4	154.7
80°	107.6	111.7	117.0	115.7	121.1	119.7	119.7	117.0	117.0	113.0	115.7
82.5°	71.3	75.3	76.7	75.3	76.7	79.4	80.7	79.4	79.4	76.7	78.0
85°	37.7	37.7	40.4	41.7	40.4	40.4	41.7	45.7	43.0	40.4	43.0
87.5°	12.1	10.8	10.8	12.1	10.8	10.8	12.1	12.1	13.5	13.5	13.5
90°	27.5	28.5	27.5	28.5	29.5	28.5	29.5	28.5	27.5	28.5	27.5
92.5°	62.4	59.0	57.0	53.1	54.0	52.1	54.0	53.1	57.0	59.0	62.4
95°	170.0	152.3	133.6	124.8	117.9	114.0	117.9	124.8	133.6	152.3	170.0
97.5°	427.4	371.4	305.6	268.3	244.7	233.9	244.7	268.3	305.6	371.4	427.4
100°	894.2	824.4	725.2	653.4	615.1	616.1	615.1	653.4	725.2	824.4	894.2
102.5°	1197.3	1159.5	1087.8	1034.7	1004.2	975.7	1004.2	1034.7	1087.8	1159.5	1197.3
105°	1381.6	1368.8	1323.6	1286.2	1254.8	1249.9	1254.8	1286.2	1323.6	1368.8	1381.6
107.5°	1462.6	1475.9	1470.0	1452.3	1439.5	1428.7	1439.5	1452.3	1470.0	1475.9	1462.6
110°	1465.1	1499.5	1527.0	1534.8	1532.9	1530.9	1532.9	1534.8	1527.0	1499.5	1465.1

TEST NUMBER: P1011048

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1409.6	1456.2	1512.2	1540.7	1550.6	1551.5	1550.6	1540.7	1512.2	1456.2	1409.6
115°	1325.0	1378.6	1452.3	1495.5	1515.2	1520.1	1515.2	1495.5	1452.3	1378.6	1325.0
117.5°	1234.6	1290.2	1366.8	1415.0	1444.4	1451.3	1444.4	1415.0	1366.8	1290.2	1234.6
120°	1149.2	1198.8	1276.4	1331.4	1355.0	1360.9	1355.0	1331.4	1276.4	1198.8	1149.2
122.5°	1081.9	1127.1	1193.9	1242.0	1268.6	1276.4	1268.6	1242.0	1193.9	1127.1	1081.9
125°	1021.9	1061.2	1124.1	1167.3	1191.9	1198.8	1191.9	1167.3	1124.1	1061.2	1021.9
127.5°	972.8	1009.1	1066.1	1103.5	1126.1	1132.0	1126.1	1103.5	1066.1	1009.1	972.8
130°	927.6	961.0	1013.1	1048.4	1069.1	1076.9	1069.1	1048.4	1013.1	961.0	927.6
132.5°	885.4	916.8	964.9	1000.3	1018.0	1022.9	1018.0	1000.3	964.9	916.8	885.4
135°	841.6	869.6	917.8	947.2	964.9	971.8	964.9	947.2	917.8	869.6	841.6
137.5°	800.3	825.4	866.7	897.1	911.9	917.8	911.9	897.1	866.7	825.4	800.3
140°	760.0	781.2	818.5	846.0	861.8	860.8	861.8	846.0	818.5	781.2	760.0
142.5°	723.2	740.9	771.4	794.9	808.7	807.7	808.7	794.9	771.4	740.9	723.2
145°	690.2	704.5	729.1	749.7	757.6	759.6	757.6	749.7	729.1	704.5	690.2
147.5°	664.8	675.1	694.7	709.4	717.3	718.3	717.3	709.4	694.7	675.1	664.8
150°	642.2	651.5	666.2	677.0	682.9	682.9	682.9	677.0	666.2	651.5	642.2
152.5°	622.5	629.9	640.7	650.5	653.4	653.4	653.4	650.5	640.7	629.9	622.5
155°	604.3	610.2	619.0	626.9	628.9	629.9	628.9	626.9	619.0	610.2	604.3
157.5°	586.6	591.5	599.4	605.3	607.3	607.3	607.3	605.3	599.4	591.5	586.6
160°	570.4	573.8	580.7	586.6	586.6	585.6	586.6	586.6	580.7	573.8	570.4
162.5°	555.2	558.1	562.1	567.0	567.0	566.0	567.0	567.0	562.1	558.1	555.2
165°	540.0	542.4	546.3	550.3	549.3	549.3	549.3	550.3	546.3	542.4	540.0
167.5°	526.7	528.6	530.6	533.6	532.6	532.6	532.6	533.6	530.6	528.6	526.7
170°	514.9	515.9	516.9	518.8	517.8	517.8	517.8	518.8	516.9	515.9	514.9
172.5°	504.6	505.1	505.1	507.0	505.1	504.1	505.1	507.0	505.1	505.1	504.6
175°	495.2	495.2	495.2	496.2	495.2	494.3	495.2	496.2	495.2	495.2	495.2
177.5°	489.3	489.3	488.4	489.3	487.4	487.4	487.4	489.3	488.4	489.3	489.3
180°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4

TEST NUMBER: P1011048

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1318.3	1321.0	1322.3	1317.0	1312.9	1319.7	1329.1	1335.8	1341.2	1347.9	1351.9
5°	1240.3	1249.7	1249.7	1252.4	1256.4	1263.2	1280.6	1292.8	1303.5	1311.6	1318.3
7.5°	1174.4	1181.1	1185.1	1191.9	1198.6	1208.0	1228.2	1245.7	1261.8	1271.2	1282.0
10°	1115.2	1120.6	1127.3	1131.3	1143.4	1156.9	1182.4	1197.2	1216.1	1230.9	1244.3
12.5°	1058.7	1077.5	1081.6	1080.2	1091.0	1105.8	1131.3	1154.2	1174.4	1189.2	1204.0
15°	1018.3	1025.1	1033.1	1031.8	1054.6	1058.7	1080.2	1107.1	1134.0	1143.4	1156.9
17.5°	973.9	984.7	992.8	996.8	1003.5	1018.3	1038.5	1058.7	1093.7	1095.0	1130.0
20°	939.0	949.7	955.1	960.5	964.5	982.0	999.5	1022.4	1050.6	1065.4	1084.2
22.5°	916.1	921.5	925.5	929.5	934.9	944.3	965.9	991.4	1010.3	1026.4	1038.5
25°	889.2	894.6	899.9	902.6	906.7	912.1	928.2	948.4	975.3	986.0	998.2
27.5°	870.4	870.4	873.0	873.0	878.4	883.8	895.9	914.7	936.3	949.7	965.9
30°	850.2	848.8	850.2	848.8	847.5	855.6	866.3	882.5	897.3	913.4	924.2
32.5°	830.0	828.7	828.7	830.0	824.6	828.7	834.0	848.8	865.0	873.0	885.2
35°	808.5	805.8	805.8	805.8	803.1	800.4	805.8	819.2	830.0	840.8	850.2
37.5°	787.0	782.9	782.9	780.2	777.5	773.5	773.5	784.3	799.1	803.1	815.2
40°	757.4	757.4	754.7	753.3	750.6	747.9	743.9	753.3	766.8	770.8	780.2
42.5°	727.8	723.7	722.4	722.4	722.4	718.3	715.7	722.4	730.5	737.2	742.6
45°	694.1	691.4	692.8	691.4	688.8	687.4	686.1	688.8	698.2	700.9	707.6
47.5°	657.8	656.5	656.5	655.1	653.8	655.1	649.7	656.5	659.2	661.8	667.2
50°	620.1	618.8	617.5	616.1	616.1	617.5	616.1	616.1	621.5	624.2	629.6
52.5°	582.5	578.4	578.4	577.1	577.1	574.4	577.1	578.4	581.1	583.8	586.5
55°	542.1	542.1	538.1	538.1	535.4	535.4	536.7	535.4	540.8	543.5	543.5
57.5°	503.1	497.7	499.1	496.4	493.7	492.3	492.3	495.0	497.7	497.7	500.4
60°	461.4	456.0	454.7	449.3	452.0	448.0	449.3	449.3	454.7	452.0	454.7
62.5°	419.7	413.0	408.9	406.3	406.3	407.6	404.9	403.6	406.3	408.9	414.3
65°	375.3	371.3	367.2	363.2	363.2	361.9	364.6	360.5	359.2	360.5	363.2
67.5°	329.6	325.5	321.5	317.5	318.8	314.8	312.1	316.1	313.4	314.8	317.5
70°	285.2	282.5	274.4	271.7	270.4	271.7	270.4	267.7	271.7	270.4	271.7
72.5°	240.8	238.1	234.1	227.3	227.3	226.0	224.7	224.7	223.3	223.3	223.3
75°	197.7	192.4	188.3	187.0	184.3	182.9	181.6	178.9	180.3	181.6	178.9
77.5°	153.4	146.6	145.3	145.3	141.2	141.2	142.6	141.2	139.9	139.9	139.9
80°	113.0	107.6	107.6	104.9	102.2	102.2	102.2	102.2	100.9	99.5	100.9
82.5°	72.6	71.3	70.0	70.0	72.6	67.3	70.0	68.6	67.3	67.3	65.9
85°	40.4	41.7	40.4	41.7	39.0	40.4	40.4	40.4	39.0	40.4	37.7
87.5°	14.8	14.8	14.8	16.1	16.1	16.1	16.1	16.1	17.5	16.1	16.1
90°	26.5	25.5	24.6	23.6	24.6	21.6	18.7	15.7	12.8	11.8	10.8
92.5°	65.8	75.7	97.3	136.6	182.8	202.4	151.3	99.2	67.8	59.0	50.1
95°	187.7	239.8	353.7	472.6	582.7	518.8	357.7	211.3	127.7	108.6	89.4
97.5°	483.4	613.2	812.6	926.6	896.1	669.2	398.0	228.0	145.4	124.3	103.2
100°	963.9	1078.9	1158.5	1124.1	930.5	628.9	370.4	225.0	156.2	137.0	117.9
102.5°	1235.1	1290.2	1273.5	1133.9	866.7	569.9	346.9	228.9	169.0	151.8	134.6
105°	1394.3	1375.7	1277.4	1072.0	790.0	523.7	338.0	236.8	183.7	168.5	153.3
107.5°	1449.4	1372.7	1218.4	983.6	722.2	490.3	336.1	249.6	202.4	188.2	173.9
110°	1430.7	1306.9	1126.1	901.1	666.2	472.6	341.0	266.3	222.1	208.4	194.6

TEST NUMBER: P1011048

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1362.9	1220.4	1034.7	829.3	628.9	462.8	350.8	283.0	242.7	229.4	216.2
115°	1271.5	1127.1	956.1	774.3	604.3	461.8	361.6	301.7	264.3	251.0	237.8
117.5°	1179.1	1046.5	895.2	737.9	587.6	462.8	375.4	321.3	284.0	271.7	259.4
120°	1099.5	981.6	849.0	710.4	576.8	466.7	391.1	340.0	304.6	292.3	280.0
122.5°	1036.7	929.6	812.6	687.8	569.9	473.6	405.8	359.6	325.2	312.0	298.7
125°	982.6	888.3	781.2	669.2	564.0	480.5	421.5	378.3	343.9	330.6	317.4
127.5°	936.4	850.0	752.7	651.5	561.1	488.4	434.3	395.0	361.6	348.4	335.1
130°	894.2	814.6	726.2	637.7	558.1	496.2	447.1	409.7	377.3	364.0	350.8
132.5°	853.9	781.2	701.6	624.9	557.1	502.1	458.9	422.5	391.1	378.3	365.5
135°	813.6	749.7	680.0	614.1	556.2	508.0	468.7	435.3	404.8	391.6	378.3
137.5°	775.3	718.3	659.3	604.3	554.2	511.9	476.6	444.1	414.7	402.4	390.1
140°	738.9	691.8	641.6	595.5	553.2	515.9	482.5	453.0	424.5	412.2	399.9
142.5°	705.5	666.2	624.9	587.6	551.2	518.8	488.4	459.9	432.4	421.0	409.7
145°	676.0	644.6	612.2	580.7	549.3	519.8	492.3	465.8	440.2	428.9	417.6
147.5°	654.4	627.9	601.4	573.8	546.3	519.8	495.2	470.7	447.1	437.2	427.4
150°	632.8	612.2	589.6	567.0	542.4	519.8	496.2	475.6	453.0	444.2	435.3
152.5°	615.1	597.4	578.8	559.1	537.5	516.9	498.2	478.5	459.9	451.6	443.2
155°	598.4	583.7	568.0	551.2	531.6	514.9	498.2	482.5	465.8	458.9	452.0
157.5°	581.7	569.9	556.2	542.4	526.7	511.9	499.2	484.4	470.7	465.3	459.9
160°	567.0	557.1	546.3	533.6	520.8	510.0	499.2	487.4	475.6	470.7	465.8
162.5°	552.2	543.4	534.5	524.7	514.9	506.0	498.2	488.4	478.5	474.6	470.7
165°	537.5	530.6	524.7	516.9	509.0	502.1	496.2	489.3	481.5	478.0	474.6
167.5°	524.7	520.8	515.9	509.0	503.1	498.2	495.2	489.3	483.4	481.0	478.5
170°	513.9	510.0	507.0	502.1	497.2	494.3	492.3	488.4	483.4	482.4	481.5
172.5°	504.1	501.1	499.2	495.2	492.3	491.3	491.3	488.4	484.4	483.9	483.4
175°	495.2	493.3	492.3	490.3	488.4	488.4	489.3	487.4	485.4	484.9	484.4
177.5°	489.3	488.4	487.4	486.4	485.4	486.4	488.4	486.4	485.4	485.4	485.4
180°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4

TEST NUMBER: P1011048

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1388.3	1388.3	1388.3	1388.3
2.5°	1358.7	1362.7	1376.2	1392.3
5°	1331.8	1342.5	1361.4	1386.9
7.5°	1302.2	1318.3	1345.2	1377.5
10°	1268.5	1291.4	1325.0	1365.4
12.5°	1232.2	1261.8	1304.9	1346.6
15°	1209.3	1238.9	1278.0	1323.7
17.5°	1165.0	1199.9	1240.3	1304.9
20°	1119.2	1158.2	1210.7	1275.3
22.5°	1084.2	1125.9	1175.7	1244.3
25°	1042.5	1085.6	1139.4	1210.7
27.5°	998.2	1041.2	1101.7	1177.1
30°	964.5	1006.2	1064.1	1144.8
32.5°	924.2	964.5	1025.1	1109.8
35°	878.4	924.2	982.0	1068.1
37.5°	843.5	885.2	945.7	1027.7
40°	805.8	842.1	901.3	982.0
42.5°	765.4	805.8	856.9	937.6
45°	727.8	757.4	809.8	886.5
47.5°	687.4	721.0	761.4	820.6
50°	644.4	672.6	717.0	757.4
52.5°	602.7	625.5	663.2	694.1
55°	558.3	581.1	609.4	628.2
57.5°	516.6	532.7	551.5	563.6
60°	465.4	481.6	493.7	505.8
62.5°	419.7	431.8	438.5	445.3
65°	372.6	379.4	383.4	388.8
67.5°	321.5	328.2	329.6	337.6
70°	274.4	275.8	278.5	282.5
72.5°	230.0	232.7	231.4	234.1
75°	184.3	187.0	184.3	187.0
77.5°	139.9	142.6	142.6	146.6
80°	100.9	102.2	103.6	103.6
82.5°	65.9	70.0	67.3	68.6
85°	37.7	39.0	39.0	40.4
87.5°	17.5	18.8	17.5	20.2
90°	8.8	5.9	3.9	2.0
92.5°	40.3	31.4	21.6	14.7
95°	63.9	47.2	36.4	33.4
97.5°	77.6	62.9	54.0	53.1
100°	94.3	80.6	73.7	72.7
102.5°	114.0	101.2	95.3	93.3
105°	134.6	122.8	116.9	114.0
107.5°	156.2	144.4	138.5	135.6
110°	177.9	167.0	162.1	159.2

TEST NUMBER: P1011048

CATALOG NUMBER: S123DIP-B1000D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	199.5	188.7	183.7	180.8
115°	221.1	211.3	205.4	201.4
117.5°	240.7	231.9	227.0	222.1
120°	261.4	251.5	246.6	243.7
122.5°	281.0	270.2	265.3	262.4
125°	298.7	287.9	282.0	280.0
127.5°	314.4	303.6	296.7	293.8
130°	330.2	318.4	309.5	306.6
132.5°	344.9	330.2	320.3	316.4
135°	357.7	342.9	332.1	328.2
137.5°	369.5	353.7	342.9	339.0
140°	380.3	364.5	354.7	349.8
142.5°	390.1	376.3	365.5	361.6
145°	400.9	386.2	377.3	374.4
147.5°	410.7	398.0	389.1	387.1
150°	421.5	408.8	400.9	399.9
152.5°	431.4	420.6	412.7	412.7
155°	441.2	431.4	425.5	425.5
157.5°	450.0	441.2	436.3	435.3
160°	458.9	451.0	447.1	447.1
162.5°	464.8	458.9	455.9	455.9
165°	470.7	465.8	463.8	464.8
167.5°	475.6	471.7	470.7	471.7
170°	479.5	476.6	475.6	477.6
172.5°	482.5	480.5	480.5	481.5
175°	484.4	482.5	483.4	484.4
177.5°	485.4	484.4	485.4	486.4
180°	485.4	485.4	485.4	485.4

(END OF REPORT)