

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011075

Luminaire Tested: S123DIP-B1000D1195UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011075
REPORT IS A COMBINATION OF REPORTS P989105 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D1195UB30-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8532.0 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011075

CATALOG NUMBER: S123DIP-B1000D1195UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1011075

CATALOG NUMBER: S123DIP-B1000D1195UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	94	90	87	90	87	83	80	73	71	69	61	59	58	50	49	48
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40
3	82	72	65	59	75	67	61	56	57	52	48	48	44	41	39	37	35
4	75	64	56	50	69	60	53	47	51	46	41	43	39	36	35	32	30
5	69	57	49	43	63	53	46	41	46	40	36	38	34	31	32	29	26
6	63	51	43	38	58	48	41	36	41	35	31	35	30	27	29	26	23
7	59	46	39	33	54	43	36	31	37	32	28	32	27	24	26	23	21
8	54	42	34	29	50	39	32	28	34	28	25	29	25	22	24	21	18
9	51	38	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17
10	47	35	28	23	44	33	27	22	29	23	20	25	20	17	21	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15029	15029	15029	15029
5°	15039	17316	15082	12923
10°	14943	20955	14958	11285
15°	14737	24851	14856	10158
20°	14559	28611	14590	9348
25°	14294	29332	14326	8925
30°	14106	24234	14106	8647
35°	13872	16208	13786	8402
40°	13592	11700	13425	8027
45°	13241	9267	12860	7561
50°	12386	7870	11945	7103
55°	11448	6916	10982	6593
60°	10497	6022	9937	6056
65°	9452	5156	8995	5341
70°	8366	4281	7810	4503
75°	7155	3228	6691	3475
80°	5657	2154	5217	2283
85°	3900	989	3122	900

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 24237 cd/sqm

TEST NUMBER: P1011075

CATALOG NUMBER: S123DIP-B1000D1195UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.3	1.6
10°-20°	441.0	5.2
20°-30°	742.1	8.7
30°-40°	838.6	9.8
40°-50°	751.1	8.8
50°-60°	606.3	7.1
60°-70°	422.5	5.0
70°-80°	221.8	2.6
80°-90°	56.3	0.7
90°-100°	311.3	3.6
100°-110°	911.3	10.7
110°-120°	889.9	10.4
120°-130°	708.7	8.3
130°-140°	559.2	6.6
140°-150°	417.1	4.9
150°-160°	290.9	3.4
160°-170°	170.9	2.0
170°-180°	55.6	0.7
0°-30°	1320.4	15.5
0°-40°	2159.1	25.3
0°-60°	3516.5	41.2
0°-90°	4217.2	49.4
90°-120°	2112.5	24.8
90°-150°	3797.6	44.5
90°-180°	4315.0	50.6
0°-180°	8532.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1396	1396	1396	1396	1396	
5°	1395	1659	1399	1238	1395	132
15°	1331	2469	1342	1009	1331	376
25°	1218	2930	1220	892	1218	562
35°	1074	1579	1068	818	1074	672
45°	892	852	866	695	892	682
55°	632	579	606	552	632	566
65°	391	376	372	390	391	389
75°	188	194	176	208	188	202
85°	41	45	32	41	41	47
90°	2	34	2	34	2	6
95°	40	135	40	135	40	42
105°	135	1477	135	1477	135	143
115°	238	1796	238	1796	238	236
125°	331	1417	331	1417	331	294
135°	388	1148	388	1148	388	300
145°	442	898	442	898	442	277
155°	503	744	503	744	503	231
165°	549	649	549	649	549	155
175°	572	584	572	584	572	54
180°	574	574	574	574	574	

TEST NUMBER: P1011075

CATALOG NUMBER: S123DIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2
2.5°	1400.3	1411.1	1416.5	1424.6	1432.7	1444.9	1449.0	1455.7	1453.0	1458.4	1461.2
5°	1394.9	1413.8	1430.0	1450.3	1469.3	1482.8	1496.3	1518.0	1534.2	1536.9	1549.1
7.5°	1385.4	1412.4	1440.9	1469.3	1505.8	1527.4	1551.8	1581.6	1605.9	1645.2	1660.0
10°	1373.2	1411.1	1451.7	1490.9	1541.0	1574.8	1604.6	1654.6	1704.7	1745.3	1783.2
12.5°	1354.3	1401.6	1454.4	1512.6	1577.5	1616.7	1657.3	1723.6	1799.4	1861.6	1902.2
15°	1331.3	1390.8	1458.4	1520.7	1592.4	1665.4	1708.7	1783.2	1891.4	1949.6	2053.7
17.5°	1312.3	1373.2	1440.9	1538.3	1635.7	1708.7	1739.9	1876.5	1950.9	2048.3	2166.0
20°	1282.6	1359.7	1446.3	1543.7	1669.5	1714.2	1777.7	1915.7	2007.7	2134.9	2279.7
22.5°	1251.5	1334.0	1438.2	1539.6	1680.3	1727.7	1814.3	1923.9	2070.0	2195.8	2355.4
25°	1217.6	1306.9	1412.4	1532.9	1670.9	1739.9	1821.0	1956.3	2114.6	2272.9	2420.4
27.5°	1183.8	1281.2	1390.8	1511.2	1645.2	1726.3	1807.5	1948.2	2151.1	2323.0	2511.0
30°	1151.3	1248.7	1358.3	1481.4	1622.2	1700.6	1777.7	1953.6	2179.6	2373.0	2562.4
32.5°	1116.2	1216.3	1331.3	1434.1	1576.2	1660.0	1746.6	1953.6	2197.1	2402.8	2576.0
35°	1074.2	1177.0	1275.8	1378.6	1519.3	1612.7	1710.1	1940.1	2213.4	2412.3	2519.1
37.5°	1033.6	1124.3	1209.5	1309.6	1457.1	1557.2	1669.5	1923.9	2205.3	2371.7	2401.4
40°	987.6	1078.3	1147.3	1240.6	1396.2	1512.6	1626.2	1902.2	2170.1	2275.6	2189.0
42.5°	943.0	1014.7	1074.2	1164.9	1334.0	1447.6	1570.7	1863.0	2101.1	2122.7	1927.9
45°	891.6	943.0	995.7	1098.6	1266.3	1382.7	1519.3	1806.1	1990.1	1927.9	1681.7
47.5°	825.3	871.3	929.5	1024.2	1194.6	1315.0	1444.9	1733.1	1829.1	1699.3	1430.0
50°	761.7	800.9	855.0	947.0	1118.9	1236.6	1374.6	1618.1	1665.4	1461.2	1232.5
52.5°	698.1	727.9	780.6	872.6	1044.5	1158.1	1283.9	1500.4	1473.3	1254.2	1051.2
55°	631.8	657.5	707.6	798.2	957.9	1066.1	1186.5	1355.6	1285.3	1076.9	914.6
57.5°	566.9	593.9	645.3	721.1	871.3	976.8	1072.9	1205.5	1099.9	933.5	790.1
60°	508.7	531.7	570.9	645.3	782.0	867.2	955.2	1045.8	957.9	796.9	687.3
62.5°	447.8	469.5	506.0	573.6	691.3	767.1	837.5	911.9	814.5	696.8	599.3
65°	391.0	408.6	442.4	504.6	600.7	662.9	719.8	771.2	692.7	584.5	511.4
67.5°	339.6	354.5	382.9	438.3	519.5	564.2	610.2	653.5	587.2	500.6	438.3
70°	284.1	296.3	322.0	362.6	427.5	473.5	507.3	539.8	480.3	411.3	369.3
72.5°	235.4	247.6	263.8	305.8	350.4	378.8	415.3	432.9	399.1	342.3	300.3
75°	188.1	197.5	212.4	239.5	281.4	300.3	323.3	336.9	305.8	267.9	242.2
77.5°	147.5	151.5	162.4	181.3	209.7	231.3	248.9	257.1	235.4	211.1	189.4
80°	104.2	109.6	117.7	133.9	155.6	162.4	173.2	182.6	169.1	147.5	133.9
82.5°	69.0	75.8	79.8	86.6	100.1	108.2	110.9	119.1	106.9	98.8	93.4
85°	40.6	43.3	44.6	48.7	55.5	59.5	63.6	64.9	62.2	60.9	55.5
87.5°	20.3	20.3	20.3	23.0	24.4	27.1	28.4	28.4	28.4	27.1	25.7
90°	2.3	4.6	7.0	10.5	12.8	14.0	15.1	18.6	22.1	25.5	29.0
92.5°	17.4	25.5	37.2	47.6	59.2	69.6	80.1	117.3	178.8	239.2	216.0
95°	39.5	43.0	55.7	75.5	105.7	128.4	151.0	249.7	422.7	613.1	688.6
97.5°	62.7	63.9	74.3	91.7	121.9	146.9	171.9	269.4	470.3	790.8	1059.0
100°	85.9	87.1	95.2	111.5	139.3	162.0	184.6	265.9	437.8	743.2	1099.6
102.5°	110.3	112.6	119.6	134.7	159.1	179.4	199.7	270.6	409.9	673.5	1024.2
105°	134.7	138.2	145.1	159.1	181.1	199.1	217.1	279.8	399.4	618.9	933.6
107.5°	160.2	163.7	170.7	184.6	205.5	222.4	239.2	294.9	397.1	579.4	853.5
110°	188.1	191.6	197.4	210.2	229.9	246.2	262.4	314.7	402.9	558.5	787.3

TEST NUMBER: P1011075

CATALOG NUMBER: S123DIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	213.7	217.1	222.9	235.7	255.5	271.2	286.8	334.4	414.5	546.9	743.2
115°	238.0	242.7	249.7	261.3	281.0	296.7	312.4	356.5	427.3	545.8	714.1
117.5°	262.4	268.2	274.0	284.5	306.5	321.0	335.6	379.7	443.6	546.9	694.4
120°	288.0	291.5	297.3	308.9	330.9	345.4	360.0	401.8	462.1	551.6	681.6
122.5°	310.0	313.5	319.3	332.1	353.0	368.6	384.3	425.0	479.6	559.7	673.5
125°	330.9	333.3	340.2	353.0	375.1	390.8	406.4	447.1	498.1	567.8	666.5
127.5°	347.2	350.7	358.8	371.6	396.0	411.6	427.3	466.8	513.2	577.1	663.0
130°	362.3	365.8	376.2	390.2	414.5	430.2	445.9	484.2	528.3	586.4	659.5
132.5°	373.9	378.5	390.2	407.6	432.0	447.0	462.1	499.3	542.3	593.4	658.4
135°	387.8	392.5	405.2	422.7	447.1	462.8	478.4	514.4	553.9	600.3	657.2
137.5°	400.6	405.2	418.0	436.6	461.0	475.5	490.0	524.9	563.2	605.0	654.9
140°	413.4	419.2	430.8	449.4	472.6	487.1	501.6	535.3	570.1	609.6	653.7
142.5°	427.3	432.0	444.7	461.0	484.2	497.6	510.9	543.4	577.1	613.1	651.4
145°	442.4	445.9	456.3	473.8	493.5	506.8	520.2	550.4	581.7	614.3	649.1
147.5°	457.5	459.8	470.3	485.4	505.1	516.7	528.3	556.2	585.2	614.3	645.6
150°	472.6	473.8	483.0	498.1	514.4	524.8	535.3	562.0	586.4	614.3	641.0
152.5°	487.7	487.7	497.0	509.8	523.7	533.6	543.4	565.5	588.7	610.8	635.2
155°	502.8	502.8	509.8	521.4	534.1	542.2	550.4	570.1	588.7	608.5	628.2
157.5°	514.4	515.6	521.4	531.8	543.4	549.8	556.2	572.5	589.9	605.0	622.4
160°	528.3	528.3	533.0	542.3	550.4	556.2	562.0	575.9	589.9	602.6	615.4
162.5°	538.8	538.8	542.3	549.2	556.2	560.8	565.5	577.1	588.7	598.0	608.5
165°	549.2	548.1	550.4	556.2	560.8	564.9	569.0	578.3	586.4	593.4	601.5
167.5°	557.4	556.2	557.4	562.0	565.5	568.4	571.3	578.3	585.2	588.7	594.5
170°	564.3	562.0	563.2	566.7	569.0	570.2	571.3	577.1	581.7	584.1	587.6
172.5°	569.0	567.8	567.8	570.1	571.3	571.9	572.5	577.1	580.6	580.6	581.7
175°	572.5	571.3	570.1	572.5	572.5	573.0	573.6	575.9	578.3	577.1	577.1
177.5°	574.8	573.6	572.5	573.6	573.6	573.6	573.6	574.8	577.1	574.8	573.6
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1011075

CATALOG NUMBER: S123DIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2
2.5°	1470.6	1473.3	1482.8	1489.6	1503.1	1501.7	1501.7	1500.4	1496.3	1503.1	1507.2
5°	1573.4	1596.4	1599.2	1628.9	1630.3	1642.4	1650.6	1643.8	1660.0	1658.7	1646.5
7.5°	1700.6	1731.7	1746.6	1775.0	1807.5	1799.4	1830.5	1835.9	1833.2	1846.7	1856.2
10°	1840.0	1894.1	1932.0	1984.7	1998.3	2006.4	2026.7	2044.3	2079.4	2052.4	2070.0
12.5°	1999.6	2038.9	2088.9	2172.8	2214.7	2241.8	2251.3	2263.4	2287.8	2272.9	2274.3
15°	2133.6	2186.3	2271.6	2375.7	2387.9	2421.7	2413.6	2486.7	2521.8	2469.1	2498.8
17.5°	2272.9	2343.3	2444.7	2535.4	2586.8	2609.8	2631.4	2701.8	2699.1	2691.0	2697.7
20°	2362.2	2477.2	2603.0	2723.4	2738.3	2755.9	2814.1	2843.8	2838.4	2861.4	2876.3
22.5°	2488.0	2609.8	2743.7	2823.5	2857.4	2877.7	2923.7	2942.6	2950.7	2956.1	2946.7
25°	2593.5	2723.4	2822.2	2892.5	2912.8	2923.7	2938.5	2944.0	2939.9	2930.4	2938.5
27.5°	2665.3	2769.4	2837.1	2869.5	2858.7	2841.1	2812.7	2793.8	2751.8	2731.5	2755.9
30°	2695.0	2741.0	2761.3	2707.2	2653.1	2609.8	2555.7	2455.6	2377.1	2400.1	2369.0
32.5°	2647.7	2617.9	2520.5	2381.1	2339.2	2268.8	2116.0	1998.3	2002.3	1940.1	1965.8
35°	2508.3	2373.0	2189.0	1978.0	1922.5	1884.6	1716.9	1691.2	1637.0	1578.9	1595.1
37.5°	2262.1	2064.6	1841.3	1685.7	1603.2	1520.7	1426.0	1369.2	1336.7	1312.3	1331.3
40°	1961.7	1720.9	1536.9	1397.6	1327.2	1274.5	1209.5	1152.7	1116.2	1112.1	1118.9
42.5°	1666.8	1463.9	1294.7	1162.2	1139.2	1076.9	1035.0	990.3	979.5	961.9	971.4
45°	1411.1	1246.0	1106.7	998.5	971.4	955.2	903.8	875.3	863.2	852.3	868.6
47.5°	1225.7	1052.6	951.1	886.2	859.1	832.0	803.6	784.7	775.2	776.6	775.2
50°	1047.2	920.0	830.7	780.6	764.4	745.5	722.5	710.3	706.2	694.0	703.5
52.5°	901.0	809.0	746.8	699.5	687.3	673.8	654.8	648.0	638.6	635.9	635.9
55°	783.3	711.6	661.6	630.5	615.6	604.8	593.9	585.8	579.1	579.1	579.1
57.5°	691.3	629.1	592.6	565.5	560.1	549.3	537.1	537.1	527.6	526.3	530.3
60°	612.9	557.4	529.0	506.0	497.9	495.2	483.0	483.0	480.3	473.5	478.9
62.5°	533.1	492.5	468.1	450.5	442.4	442.4	432.9	426.2	426.2	427.5	424.8
65°	460.0	430.2	408.6	395.1	391.0	385.6	384.2	378.8	374.8	376.1	374.8
67.5°	395.1	372.1	357.2	346.3	339.6	336.9	332.8	332.8	330.1	331.5	324.7
70°	336.9	313.9	301.7	290.9	288.2	288.2	282.8	284.1	281.4	285.5	282.8
72.5°	277.3	259.8	250.3	246.2	243.5	242.2	239.5	236.8	235.4	238.1	236.8
75°	224.6	209.7	202.9	200.2	197.5	197.5	196.2	194.8	193.5	193.5	193.5
77.5°	174.5	165.1	156.9	159.6	155.6	156.9	152.9	152.9	154.2	152.9	152.9
80°	128.5	121.8	121.8	119.1	113.6	116.4	116.4	112.3	110.9	113.6	109.6
82.5°	85.2	83.9	81.2	79.8	77.1	78.5	77.1	75.8	74.4	77.1	74.4
85°	50.1	50.1	48.7	46.0	48.7	47.4	46.0	46.0	44.6	44.6	44.6
87.5°	25.7	23.0	23.0	21.6	23.0	20.3	21.6	20.3	18.9	20.3	18.9
90°	27.9	29.0	30.2	31.4	32.6	33.7	32.5	33.7	34.8	33.7	34.8
92.5°	161.4	115.0	89.4	77.8	73.8	69.7	67.3	62.7	63.9	61.5	63.9
95°	558.5	418.0	283.3	221.8	200.9	180.0	157.9	147.5	139.3	134.7	139.3
97.5°	1095.0	960.3	724.6	571.3	505.1	438.9	361.1	317.0	289.1	276.4	289.1
100°	1328.4	1369.0	1275.0	1139.1	1056.6	974.2	856.9	772.2	726.9	728.1	726.9
102.5°	1340.0	1504.9	1524.6	1459.6	1414.9	1370.2	1285.4	1222.7	1186.7	1153.0	1186.7
105°	1266.8	1509.5	1625.6	1647.7	1632.6	1617.5	1564.1	1520.0	1482.8	1477.0	1482.8
107.5°	1162.3	1439.9	1622.2	1712.7	1728.4	1744.1	1737.1	1716.2	1701.1	1688.3	1701.1
110°	1064.8	1330.7	1544.4	1690.7	1731.4	1772.0	1804.5	1813.8	1811.4	1809.1	1811.4

TEST NUMBER: P1011075

CATALOG NUMBER: S123DIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	980.0	1222.7	1442.2	1610.5	1665.7	1720.9	1787.0	1820.7	1832.3	1833.5	1832.3
115°	915.0	1129.8	1331.9	1502.6	1565.8	1629.1	1716.2	1767.3	1790.5	1796.3	1790.5
117.5°	872.0	1057.8	1236.6	1393.4	1459.0	1524.6	1615.2	1672.1	1706.9	1715.1	1706.9
120°	839.5	1003.3	1160.0	1299.4	1358.0	1416.6	1508.4	1573.4	1601.3	1608.2	1601.3
122.5°	812.8	960.3	1098.5	1225.0	1278.4	1331.9	1410.8	1467.7	1499.1	1508.4	1499.1
125°	790.8	923.1	1049.7	1161.2	1207.6	1254.1	1328.4	1379.5	1408.5	1416.6	1408.5
127.5°	769.9	889.5	1004.4	1106.6	1149.6	1192.5	1259.9	1304.0	1330.7	1337.7	1330.7
130°	753.6	858.1	962.6	1056.7	1096.2	1135.6	1197.2	1239.0	1263.4	1272.6	1263.4
132.5°	738.5	829.1	923.1	1009.1	1046.2	1083.4	1140.3	1182.1	1203.0	1208.8	1203.0
135°	725.7	803.5	886.0	961.5	994.6	1027.6	1084.5	1119.4	1140.3	1148.4	1140.3
137.5°	714.1	779.1	848.8	916.2	945.8	975.4	1024.2	1060.2	1077.6	1084.5	1077.6
140°	703.7	758.2	817.5	873.2	898.2	923.1	967.3	999.8	1018.3	1017.2	1018.3
142.5°	694.4	738.5	787.3	833.7	854.6	875.5	911.5	939.4	955.6	954.5	955.6
145°	686.3	723.4	761.7	798.9	815.8	832.6	861.6	886.0	895.3	897.6	895.3
147.5°	678.1	710.6	742.0	773.3	785.5	797.7	820.9	838.4	847.7	848.8	847.7
150°	670.0	696.7	723.4	747.8	758.8	769.9	787.3	800.0	807.0	807.0	807.0
152.5°	660.7	683.9	706.0	726.9	735.6	744.3	757.1	768.7	772.2	772.2	772.2
155°	651.4	671.2	689.7	707.2	714.2	721.1	731.5	740.8	743.2	744.3	743.2
157.5°	641.0	657.2	673.5	687.4	693.2	699.0	708.3	715.3	717.6	717.6	717.6
160°	630.5	645.6	658.4	670.0	674.0	678.1	686.3	693.2	693.2	692.1	693.2
162.5°	620.1	631.7	642.1	652.6	656.0	659.5	664.2	670.0	670.0	668.8	670.0
165°	610.8	620.1	627.0	635.2	638.1	641.0	645.6	650.3	649.1	649.1	649.1
167.5°	601.5	609.6	615.4	620.1	622.4	624.7	627.0	630.5	629.4	629.4	629.4
170°	593.4	599.2	602.6	607.3	608.4	609.6	610.8	613.1	611.9	611.9	611.9
172.5°	585.2	589.9	592.2	595.7	596.2	596.8	596.8	599.2	596.8	595.7	596.8
175°	579.4	581.7	582.9	585.2	585.2	585.2	585.2	586.4	585.2	584.1	585.2
177.5°	574.8	575.9	577.1	578.3	578.3	578.3	577.1	578.3	575.9	575.9	575.9
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1011075

CATALOG NUMBER: S123DIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2
2.5°	1496.3	1500.4	1489.6	1486.9	1486.9	1492.3	1488.2	1451.7	1458.4	1450.3	1447.6
5°	1661.4	1653.3	1642.4	1637.0	1630.3	1611.3	1610.0	1568.0	1559.9	1532.9	1520.7
7.5°	1842.7	1835.9	1803.4	1799.4	1796.7	1779.1	1734.4	1689.8	1657.3	1626.2	1596.4
10°	2049.7	2029.4	2014.5	1984.7	1969.9	1945.5	1887.3	1845.4	1789.9	1742.6	1680.3
12.5°	2298.6	2275.6	2225.6	2203.9	2185.0	2117.3	2059.1	2011.8	1903.6	1871.1	1794.0
15°	2481.3	2432.6	2427.1	2379.8	2377.1	2302.7	2191.7	2140.3	2056.4	1937.4	1857.6
17.5°	2678.8	2635.5	2601.7	2544.8	2536.7	2466.4	2385.2	2259.4	2167.4	2053.7	1952.3
20°	2823.5	2800.5	2742.4	2719.4	2672.0	2612.5	2528.6	2373.0	2260.7	2147.1	2022.6
22.5°	2938.5	2915.5	2869.5	2838.4	2811.4	2734.3	2634.1	2501.6	2347.3	2198.5	2070.0
25°	2937.2	2930.4	2911.5	2896.6	2876.3	2819.5	2735.6	2608.4	2436.6	2272.9	2094.3
27.5°	2770.8	2789.7	2822.2	2838.4	2834.4	2826.3	2778.9	2672.0	2517.8	2323.0	2122.7
30°	2424.4	2493.4	2554.3	2635.5	2659.8	2719.4	2746.4	2685.5	2562.4	2381.1	2159.3
32.5°	2010.4	2110.6	2243.1	2287.8	2364.9	2479.9	2608.4	2631.4	2554.3	2415.0	2182.3
35°	1649.2	1731.7	1834.6	1904.9	1973.9	2160.6	2323.0	2463.7	2489.4	2397.4	2176.9
37.5°	1365.1	1423.3	1513.9	1573.4	1637.0	1796.7	2024.0	2206.6	2335.1	2337.8	2162.0
40°	1159.5	1185.2	1263.6	1306.9	1367.8	1505.8	1708.7	1946.9	2134.9	2221.5	2122.7
42.5°	982.2	1016.0	1081.0	1113.5	1152.7	1273.1	1407.0	1633.0	1865.7	2051.0	2049.7
45°	876.7	901.0	930.8	957.9	1002.5	1074.2	1227.1	1396.2	1619.4	1829.1	1911.7
47.5°	783.3	806.3	836.1	844.2	874.0	941.6	1035.0	1182.5	1390.8	1599.2	1754.7
50°	704.9	723.8	744.1	759.0	772.5	828.0	898.3	1022.8	1189.2	1390.8	1584.3
52.5°	644.0	657.5	675.1	683.2	695.4	736.0	790.1	882.1	1018.7	1202.7	1390.8
55°	587.2	596.6	607.5	621.0	626.4	656.2	698.1	776.6	878.0	1043.1	1221.7
57.5°	534.4	538.5	545.2	553.3	560.1	585.8	622.3	675.1	764.4	891.6	1060.7
60°	474.9	485.7	489.8	497.9	501.9	522.2	550.6	595.3	664.3	773.9	901.0
62.5°	424.8	431.6	438.3	442.4	451.9	458.6	481.6	522.2	579.1	660.2	775.2
65°	380.2	382.9	386.9	391.0	393.7	401.8	423.5	450.5	493.8	565.5	654.8
67.5°	328.8	331.5	336.9	338.2	340.9	351.8	363.9	386.9	423.5	477.6	550.6
70°	278.7	282.8	285.5	288.2	292.2	296.3	309.8	328.8	357.2	395.1	451.9
72.5°	235.4	239.5	239.5	242.2	240.8	246.2	259.8	273.3	292.2	323.3	373.4
75°	192.1	192.1	194.8	196.2	197.5	202.9	208.3	219.2	234.1	258.4	289.5
77.5°	151.5	150.2	152.9	152.9	152.9	156.9	162.4	167.8	177.2	194.8	219.2
80°	110.9	110.9	113.6	115.0	112.3	113.6	116.4	121.8	128.5	140.7	154.2
82.5°	73.1	78.5	77.1	78.5	77.1	79.8	81.2	82.5	85.2	90.6	100.1
85°	44.6	44.6	44.6	46.0	44.6	46.0	46.0	46.0	47.4	50.1	54.1
87.5°	18.9	18.9	18.9	20.3	18.9	18.9	20.3	18.9	20.3	20.3	21.6
90°	33.7	32.5	33.7	32.6	31.4	30.2	29.0	27.9	29.0	25.5	22.1
92.5°	62.7	67.3	69.7	73.8	77.8	89.4	115.0	161.4	216.0	239.2	178.8
95°	147.5	157.9	180.0	200.9	221.8	283.3	418.0	558.5	688.6	613.1	422.7
97.5°	317.0	361.1	438.9	505.1	571.3	724.6	960.3	1095.0	1059.0	790.8	470.3
100°	772.2	856.9	974.2	1056.6	1139.1	1275.0	1369.0	1328.4	1099.6	743.2	437.8
102.5°	1222.7	1285.4	1370.2	1414.9	1459.6	1524.6	1504.9	1340.0	1024.2	673.5	409.9
105°	1520.0	1564.1	1617.5	1632.6	1647.7	1625.6	1509.5	1266.8	933.6	618.9	399.4
107.5°	1716.2	1737.1	1744.1	1728.4	1712.7	1622.2	1439.9	1162.3	853.5	579.4	397.1
110°	1813.8	1804.5	1772.0	1731.4	1690.7	1544.4	1330.7	1064.8	787.3	558.5	402.9

TEST NUMBER: P1011075

CATALOG NUMBER: S123DIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1820.7	1787.0	1720.9	1665.7	1610.5	1442.2	1222.7	980.0	743.2	546.9	414.5
115°	1767.3	1716.2	1629.1	1565.8	1502.6	1331.9	1129.8	915.0	714.1	545.8	427.3
117.5°	1672.1	1615.2	1524.6	1459.0	1393.4	1236.6	1057.8	872.0	694.4	546.9	443.6
120°	1573.4	1508.4	1416.6	1358.0	1299.4	1160.0	1003.3	839.5	681.6	551.6	462.1
122.5°	1467.7	1410.8	1331.9	1278.4	1225.0	1098.5	960.3	812.8	673.5	559.7	479.6
125°	1379.5	1328.4	1254.1	1207.6	1161.2	1049.7	923.1	790.8	666.5	567.8	498.1
127.5°	1304.0	1259.9	1192.5	1149.6	1106.6	1004.4	889.5	769.9	663.0	577.1	513.2
130°	1239.0	1197.2	1135.6	1096.2	1056.7	962.6	858.1	753.6	659.5	586.4	528.3
132.5°	1182.1	1140.3	1083.4	1046.2	1009.1	923.1	829.1	738.5	658.4	593.4	542.3
135°	1119.4	1084.5	1027.6	994.6	961.5	886.0	803.5	725.7	657.2	600.3	553.9
137.5°	1060.2	1024.2	975.4	945.8	916.2	848.8	779.1	714.1	654.9	605.0	563.2
140°	999.8	967.3	923.1	898.2	873.2	817.5	758.2	703.7	653.7	609.6	570.1
142.5°	939.4	911.5	875.5	854.6	833.7	787.3	738.5	694.4	651.4	613.1	577.1
145°	886.0	861.6	832.6	815.8	798.9	761.7	723.4	686.3	649.1	614.3	581.7
147.5°	838.4	820.9	797.7	785.5	773.3	742.0	710.6	678.1	645.6	614.3	585.2
150°	800.0	787.3	769.9	758.8	747.8	723.4	696.7	670.0	641.0	614.3	586.4
152.5°	768.7	757.1	744.3	735.6	726.9	706.0	683.9	660.7	635.2	610.8	588.7
155°	740.8	731.5	721.1	714.2	707.2	689.7	671.2	651.4	628.2	608.5	588.7
157.5°	715.3	708.3	699.0	693.2	687.4	673.5	657.2	641.0	622.4	605.0	589.9
160°	693.2	686.3	678.1	674.0	670.0	658.4	645.6	630.5	615.4	602.6	589.9
162.5°	670.0	664.2	659.5	656.0	652.6	642.1	631.7	620.1	608.5	598.0	588.7
165°	650.3	645.6	641.0	638.1	635.2	627.0	620.1	610.8	601.5	593.4	586.4
167.5°	630.5	627.0	624.7	622.4	620.1	615.4	609.6	601.5	594.5	588.7	585.2
170°	613.1	610.8	609.6	608.4	607.3	602.6	599.2	593.4	587.6	584.1	581.7
172.5°	599.2	596.8	596.8	596.2	595.7	592.2	589.9	585.2	581.7	580.6	580.6
175°	586.4	585.2	585.2	585.2	585.2	582.9	581.7	579.4	577.1	577.1	578.3
177.5°	578.3	577.1	578.3	578.3	578.3	577.1	575.9	574.8	573.6	574.8	577.1
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1011075

CATALOG NUMBER: S123DIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2
2.5°	1434.1	1430.0	1430.0	1427.3	1419.2	1404.3	1403.0	1405.7	1397.6	1389.5	1377.3
5°	1504.4	1478.7	1470.6	1462.5	1446.3	1419.2	1408.4	1398.9	1384.0	1366.5	1347.5
7.5°	1564.0	1527.4	1516.6	1501.7	1469.3	1431.4	1407.0	1386.7	1366.5	1342.1	1319.1
10°	1638.4	1585.6	1559.9	1538.3	1493.6	1440.9	1404.3	1374.6	1342.1	1312.3	1282.6
12.5°	1722.3	1637.0	1628.9	1576.2	1524.7	1446.3	1401.6	1358.3	1315.0	1278.5	1247.4
15°	1792.6	1699.3	1665.4	1630.3	1531.5	1434.1	1390.8	1342.1	1292.0	1252.8	1206.8
17.5°	1837.3	1760.2	1688.4	1641.1	1538.3	1451.7	1367.8	1312.3	1259.6	1205.5	1167.6
20°	1891.4	1779.1	1716.9	1653.3	1551.8	1438.2	1354.3	1285.3	1220.3	1171.6	1125.6
22.5°	1945.5	1794.0	1742.6	1673.6	1554.5	1424.6	1329.9	1260.9	1186.5	1137.8	1087.7
25°	1940.1	1815.6	1730.4	1672.2	1527.4	1412.4	1301.5	1220.3	1151.3	1089.1	1039.0
27.5°	1944.1	1791.3	1704.7	1637.0	1508.5	1394.9	1271.7	1186.5	1114.8	1049.9	997.1
30°	1945.5	1754.7	1679.0	1597.8	1473.3	1352.9	1237.9	1151.3	1075.6	1005.2	957.9
32.5°	1941.4	1725.0	1630.3	1557.2	1417.9	1312.3	1198.7	1106.7	1029.6	964.6	920.0
35°	1932.0	1689.8	1580.2	1488.2	1361.0	1254.2	1162.2	1067.5	984.9	925.4	874.0
37.5°	1906.3	1651.9	1527.4	1436.8	1294.7	1186.5	1105.3	1026.9	947.0	876.7	833.4
40°	1887.3	1600.5	1474.7	1375.9	1223.0	1117.5	1049.9	975.5	897.0	833.4	791.5
42.5°	1844.0	1551.8	1420.6	1302.9	1152.7	1044.5	980.9	921.3	853.7	791.5	753.6
45°	1773.7	1499.0	1354.3	1235.2	1075.6	972.8	914.6	865.9	806.3	746.8	708.9
47.5°	1674.9	1423.3	1283.9	1164.9	999.8	895.6	837.5	800.9	753.6	703.5	671.0
50°	1568.0	1340.7	1212.2	1094.5	926.8	825.3	768.5	734.6	703.5	657.5	626.4
52.5°	1428.7	1252.8	1129.7	1017.4	848.3	750.9	700.8	676.5	644.0	611.5	584.5
55°	1293.4	1139.2	1037.7	930.8	771.2	680.5	631.8	606.1	587.2	560.1	538.5
57.5°	1136.5	1033.6	940.3	842.9	699.5	616.9	570.9	539.8	527.6	515.5	495.2
60°	991.7	913.2	837.5	756.3	625.0	550.6	506.0	481.6	469.5	461.3	447.8
62.5°	859.1	798.2	733.3	668.3	549.3	481.6	447.8	423.5	412.6	411.3	399.1
65°	731.9	688.6	635.9	572.3	478.9	419.4	386.9	372.1	359.9	359.9	350.4
67.5°	604.8	575.0	533.1	488.4	415.3	359.9	330.1	316.6	309.8	309.8	303.1
70°	503.3	483.0	445.1	405.9	342.3	300.3	277.3	265.2	261.1	262.5	257.1
72.5°	408.6	386.9	355.8	327.4	280.1	248.9	232.7	219.2	212.4	213.8	212.4
75°	316.6	305.8	278.7	257.1	219.2	197.5	182.6	175.9	170.5	171.8	169.1
77.5°	238.1	221.9	207.0	192.1	169.1	151.5	139.4	132.6	128.5	128.5	128.5
80°	162.4	159.6	147.5	139.4	120.4	106.9	97.4	96.1	92.0	92.0	92.0
82.5°	105.5	98.8	92.0	86.6	75.8	67.6	63.6	60.9	59.5	58.2	60.9
85°	58.2	54.1	51.4	46.0	41.9	37.9	33.8	32.5	31.1	32.5	31.1
87.5°	23.0	18.9	18.9	17.6	16.2	14.9	14.9	12.2	12.2	10.8	10.8
90°	18.6	15.1	14.0	12.8	10.5	7.0	4.6	2.3	4.6	7.0	10.5
92.5°	117.3	80.1	69.6	59.2	47.6	37.2	25.5	17.4	25.5	37.2	47.6
95°	249.7	151.0	128.4	105.7	75.5	55.7	43.0	39.5	43.0	55.7	75.5
97.5°	269.4	171.9	146.9	121.9	91.7	74.3	63.9	62.7	63.9	74.3	91.7
100°	265.9	184.6	162.0	139.3	111.5	95.2	87.1	85.9	87.1	95.2	111.5
102.5°	270.6	199.7	179.4	159.1	134.7	119.6	112.6	110.3	112.6	119.6	134.7
105°	279.8	217.1	199.1	181.1	159.1	145.1	138.2	134.7	138.2	145.1	159.1
107.5°	294.9	239.2	222.4	205.5	184.6	170.7	163.7	160.2	163.7	170.7	184.6
110°	314.7	262.4	246.2	229.9	210.2	197.4	191.6	188.1	191.6	197.4	210.2

TEST NUMBER: P1011075

CATALOG NUMBER: S123DIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	334.4	286.8	271.2	255.5	235.7	222.9	217.1	213.7	217.1	222.9	235.7
115°	356.5	312.4	296.7	281.0	261.3	249.7	242.7	238.0	242.7	249.7	261.3
117.5°	379.7	335.6	321.0	306.5	284.5	274.0	268.2	262.4	268.2	274.0	284.5
120°	401.8	360.0	345.4	330.9	308.9	297.3	291.5	288.0	291.5	297.3	308.9
122.5°	425.0	384.3	368.6	353.0	332.1	319.3	313.5	310.0	313.5	319.3	332.1
125°	447.1	406.4	390.8	375.1	353.0	340.2	333.3	330.9	333.3	340.2	353.0
127.5°	466.8	427.3	411.6	396.0	371.6	358.8	350.7	347.2	350.7	358.8	371.6
130°	484.2	445.9	430.2	414.5	390.2	376.2	365.8	362.3	365.8	376.2	390.2
132.5°	499.3	462.1	447.0	432.0	407.6	390.2	378.5	373.9	378.5	390.2	407.6
135°	514.4	478.4	462.8	447.1	422.7	405.2	392.5	387.8	392.5	405.2	422.7
137.5°	524.9	490.0	475.5	461.0	436.6	418.0	405.2	400.6	405.2	418.0	436.6
140°	535.3	501.6	487.1	472.6	449.4	430.8	419.2	413.4	419.2	430.8	449.4
142.5°	543.4	510.9	497.6	484.2	461.0	444.7	432.0	427.3	432.0	444.7	461.0
145°	550.4	520.2	506.8	493.5	473.8	456.3	445.9	442.4	445.9	456.3	473.8
147.5°	556.2	528.3	516.7	505.1	485.4	470.3	459.8	457.5	459.8	470.3	485.4
150°	562.0	535.3	524.8	514.4	498.1	483.0	473.8	472.6	473.8	483.0	498.1
152.5°	565.5	543.4	533.6	523.7	509.8	497.0	487.7	487.7	487.7	497.0	509.8
155°	570.1	550.4	542.2	534.1	521.4	509.8	502.8	502.8	502.8	509.8	521.4
157.5°	572.5	556.2	549.8	543.4	531.8	521.4	515.6	514.4	515.6	521.4	531.8
160°	575.9	562.0	556.2	550.4	542.3	533.0	528.3	528.3	528.3	533.0	542.3
162.5°	577.1	565.5	560.8	556.2	549.2	542.3	538.8	538.8	538.8	542.3	549.2
165°	578.3	569.0	564.9	560.8	556.2	550.4	548.1	549.2	548.1	550.4	556.2
167.5°	578.3	571.3	568.4	565.5	562.0	557.4	556.2	557.4	556.2	557.4	562.0
170°	577.1	571.3	570.2	569.0	566.7	563.2	562.0	564.3	562.0	563.2	566.7
172.5°	577.1	572.5	571.9	571.3	570.1	567.8	567.8	569.0	567.8	567.8	570.1
175°	575.9	573.6	573.0	572.5	572.5	570.1	571.3	572.5	571.3	570.1	572.5
177.5°	574.8	573.6	573.6	573.6	573.6	572.5	573.6	574.8	573.6	572.5	573.6
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1011075

CATALOG NUMBER: S123DIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2
2.5°	1374.6	1373.2	1375.9	1367.8	1354.3	1347.5	1328.6	1324.5	1323.2	1324.5	1325.9
5°	1336.7	1335.3	1331.3	1317.7	1301.5	1289.3	1266.3	1265.0	1256.9	1248.7	1252.8
7.5°	1300.2	1294.7	1286.6	1269.0	1247.4	1233.9	1214.9	1201.4	1190.6	1183.8	1178.4
10°	1263.6	1255.5	1247.4	1224.4	1197.3	1177.0	1154.0	1143.2	1131.0	1125.6	1120.2
12.5°	1216.3	1208.2	1193.3	1166.2	1150.0	1124.3	1101.3	1090.5	1083.7	1072.9	1066.1
15°	1178.4	1162.2	1154.0	1125.6	1091.8	1089.1	1047.2	1044.5	1030.9	1030.9	1020.1
17.5°	1135.1	1122.9	1108.0	1079.6	1055.3	1030.9	1009.3	1001.2	989.0	986.3	980.9
20°	1093.2	1076.9	1071.5	1043.1	1017.4	987.6	964.6	956.5	951.1	945.7	949.8
22.5°	1049.9	1036.3	1022.8	997.1	978.2	948.4	934.9	926.8	918.6	915.9	917.3
25°	1007.9	995.7	982.2	956.5	936.2	911.9	899.7	895.6	891.6	891.6	890.2
27.5°	967.3	955.2	943.0	920.0	899.7	882.1	872.6	868.6	864.5	867.2	869.9
30°	925.4	914.6	903.8	883.5	867.2	851.0	845.6	842.9	841.5	848.3	848.3
32.5°	887.5	878.0	869.9	851.0	834.8	821.2	817.2	818.5	819.9	823.9	826.6
35°	848.3	841.5	833.4	817.2	803.6	791.5	792.8	792.8	795.5	802.3	807.7
37.5°	813.1	803.6	796.9	783.3	772.5	761.7	765.8	769.8	772.5	780.6	783.3
40°	771.2	767.1	761.7	748.2	738.7	737.3	738.7	741.4	746.8	750.9	754.9
42.5°	737.3	731.9	725.2	714.3	706.2	707.6	708.9	711.6	714.3	721.1	725.2
45°	699.5	695.4	690.0	680.5	673.8	675.1	676.5	676.5	679.2	687.3	690.0
47.5°	657.5	658.9	652.1	642.6	638.6	638.6	638.6	641.3	648.0	650.8	652.1
50°	616.9	614.2	612.9	603.4	600.7	599.3	600.7	602.0	611.5	610.2	614.2
52.5°	573.6	573.6	572.3	566.9	562.8	562.8	560.1	566.9	569.6	572.3	576.3
55°	531.7	527.6	526.3	523.6	518.2	516.8	519.5	527.6	530.3	533.1	537.1
57.5°	485.7	485.7	483.0	478.9	478.9	478.9	478.9	484.3	488.4	491.1	499.2
60°	443.8	438.3	434.3	434.3	434.3	432.9	441.1	441.1	449.2	450.5	453.2
62.5°	393.7	391.0	388.3	389.6	388.3	391.0	393.7	399.1	400.5	404.5	408.6
65°	346.3	346.3	343.6	351.8	346.3	346.3	353.1	353.1	355.8	359.9	365.3
67.5°	300.3	301.7	299.0	299.0	301.7	303.1	304.4	309.8	311.2	316.6	323.3
70°	253.0	255.7	257.1	254.3	257.1	259.8	262.5	263.8	269.2	271.9	276.0
72.5°	211.1	213.8	209.7	211.1	212.4	215.1	216.5	219.2	221.9	230.0	232.7
75°	169.1	167.8	166.4	171.8	169.1	174.5	175.9	175.9	178.6	185.4	188.1
77.5°	129.9	129.9	131.2	128.5	132.6	131.2	132.6	136.6	140.7	140.7	151.5
80°	90.6	93.4	93.4	93.4	94.7	96.1	93.4	100.1	101.5	101.5	105.5
82.5°	58.2	59.5	58.2	60.9	60.9	63.6	62.2	63.6	66.3	69.0	70.4
85°	31.1	31.1	33.8	33.8	32.5	33.8	32.5	33.8	36.5	36.5	37.9
87.5°	10.8	10.8	10.8	10.8	12.2	10.8	12.2	12.2	10.8	10.8	14.9
90°	12.8	14.0	15.1	18.6	22.1	25.5	29.0	27.9	29.0	30.2	31.4
92.5°	59.2	69.6	80.1	117.3	178.8	239.2	216.0	161.4	115.0	89.4	77.8
95°	105.7	128.4	151.0	249.7	422.7	613.1	688.6	558.5	418.0	283.3	221.8
97.5°	121.9	146.9	171.9	269.4	470.3	790.8	1059.0	1095.0	960.3	724.6	571.3
100°	139.3	162.0	184.6	265.9	437.8	743.2	1099.6	1328.4	1369.0	1275.0	1139.1
102.5°	159.1	179.4	199.7	270.6	409.9	673.5	1024.2	1340.0	1504.9	1524.6	1459.6
105°	181.1	199.1	217.1	279.8	399.4	618.9	933.6	1266.8	1509.5	1625.6	1647.7
107.5°	205.5	222.4	239.2	294.9	397.1	579.4	853.5	1162.3	1439.9	1622.2	1712.7
110°	229.9	246.2	262.4	314.7	402.9	558.5	787.3	1064.8	1330.7	1544.4	1690.7

TEST NUMBER: P1011075

CATALOG NUMBER: S123DIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	255.5	271.2	286.8	334.4	414.5	546.9	743.2	980.0	1222.7	1442.2	1610.5
115°	281.0	296.7	312.4	356.5	427.3	545.8	714.1	915.0	1129.8	1331.9	1502.6
117.5°	306.5	321.0	335.6	379.7	443.6	546.9	694.4	872.0	1057.8	1236.6	1393.4
120°	330.9	345.4	360.0	401.8	462.1	551.6	681.6	839.5	1003.3	1160.0	1299.4
122.5°	353.0	368.6	384.3	425.0	479.6	559.7	673.5	812.8	960.3	1098.5	1225.0
125°	375.1	390.8	406.4	447.1	498.1	567.8	666.5	790.8	923.1	1049.7	1161.2
127.5°	396.0	411.6	427.3	466.8	513.2	577.1	663.0	769.9	889.5	1004.4	1106.6
130°	414.5	430.2	445.9	484.2	528.3	586.4	659.5	753.6	858.1	962.6	1056.7
132.5°	432.0	447.0	462.1	499.3	542.3	593.4	658.4	738.5	829.1	923.1	1009.1
135°	447.1	462.8	478.4	514.4	553.9	600.3	657.2	725.7	803.5	886.0	961.5
137.5°	461.0	475.5	490.0	524.9	563.2	605.0	654.9	714.1	779.1	848.8	916.2
140°	472.6	487.1	501.6	535.3	570.1	609.6	653.7	703.7	758.2	817.5	873.2
142.5°	484.2	497.6	510.9	543.4	577.1	613.1	651.4	694.4	738.5	787.3	833.7
145°	493.5	506.8	520.2	550.4	581.7	614.3	649.1	686.3	723.4	761.7	798.9
147.5°	505.1	516.7	528.3	556.2	585.2	614.3	645.6	678.1	710.6	742.0	773.3
150°	514.4	524.8	535.3	562.0	586.4	614.3	641.0	670.0	696.7	723.4	747.8
152.5°	523.7	533.6	543.4	565.5	588.7	610.8	635.2	660.7	683.9	706.0	726.9
155°	534.1	542.2	550.4	570.1	588.7	608.5	628.2	651.4	671.2	689.7	707.2
157.5°	543.4	549.8	556.2	572.5	589.9	605.0	622.4	641.0	657.2	673.5	687.4
160°	550.4	556.2	562.0	575.9	589.9	602.6	615.4	630.5	645.6	658.4	670.0
162.5°	556.2	560.8	565.5	577.1	588.7	598.0	608.5	620.1	631.7	642.1	652.6
165°	560.8	564.9	569.0	578.3	586.4	593.4	601.5	610.8	620.1	627.0	635.2
167.5°	565.5	568.4	571.3	578.3	585.2	588.7	594.5	601.5	609.6	615.4	620.1
170°	569.0	570.2	571.3	577.1	581.7	584.1	587.6	593.4	599.2	602.6	607.3
172.5°	571.3	571.9	572.5	577.1	580.6	580.6	581.7	585.2	589.9	592.2	595.7
175°	572.5	573.0	573.6	575.9	578.3	577.1	577.1	579.4	581.7	582.9	585.2
177.5°	573.6	573.6	573.6	574.8	577.1	574.8	573.6	574.8	575.9	577.1	578.3
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1011075

CATALOG NUMBER: S123DIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2
2.5°	1324.5	1325.9	1320.5	1316.4	1327.2	1320.5	1320.5	1321.8	1319.1	1323.2	1321.8
5°	1250.1	1251.5	1242.0	1244.7	1239.3	1237.9	1236.6	1244.7	1243.3	1242.0	1244.7
7.5°	1177.0	1177.0	1173.0	1170.3	1170.3	1166.2	1171.6	1170.3	1173.0	1173.0	1177.0
10°	1116.2	1118.9	1112.1	1105.3	1104.0	1105.3	1105.3	1106.7	1108.0	1117.5	1116.2
12.5°	1066.1	1062.0	1060.7	1056.6	1049.9	1047.2	1044.5	1059.3	1055.3	1055.3	1055.3
15°	1010.6	1020.1	1018.7	1006.6	1003.9	1009.3	1006.6	1006.6	1020.1	1018.7	1017.4
17.5°	980.9	978.2	975.5	968.7	970.0	968.7	970.0	970.0	978.2	978.2	978.2
20°	947.0	941.6	941.6	938.9	938.9	934.9	940.3	941.6	947.0	947.0	948.4
22.5°	917.3	913.2	913.2	911.9	914.6	909.2	914.6	915.9	915.9	920.0	920.0
25°	891.6	888.9	888.9	891.6	891.6	891.6	891.6	897.0	892.9	894.3	892.9
27.5°	868.6	869.9	871.3	872.6	871.3	872.6	874.0	876.7	878.0	876.7	874.0
30°	846.9	851.0	852.3	852.3	855.0	856.4	857.8	857.8	859.1	855.0	857.8
32.5°	830.7	830.7	833.4	834.8	837.5	838.8	838.8	841.5	840.2	836.1	837.5
35°	807.7	807.7	813.1	815.8	819.9	818.5	819.9	819.9	821.2	818.5	814.5
37.5°	784.7	787.4	787.4	792.8	794.2	795.5	794.2	796.9	795.5	792.8	791.5
40°	757.6	756.3	757.6	761.7	763.0	763.0	763.0	765.8	765.8	765.8	764.4
42.5°	723.8	727.9	726.5	730.6	729.2	729.2	731.9	734.6	736.0	731.9	733.3
45°	691.3	691.3	694.0	694.0	695.4	695.4	700.8	698.1	700.8	698.1	699.5
47.5°	656.2	657.5	657.5	658.9	661.6	664.3	661.6	662.9	662.9	664.3	661.6
50°	616.9	616.9	619.6	623.7	629.1	626.4	625.0	630.5	626.4	626.4	623.7
52.5°	576.3	580.4	581.8	585.8	589.9	591.2	592.6	589.9	591.2	587.2	588.5
55°	537.1	538.5	543.9	547.9	552.0	552.0	550.6	552.0	553.3	547.9	547.9
57.5°	497.9	501.9	507.3	507.3	512.8	512.8	511.4	511.4	512.8	508.7	507.3
60°	455.9	460.0	466.8	466.8	474.9	476.2	473.5	470.8	470.8	466.8	468.1
62.5°	411.3	415.3	419.4	426.2	431.6	428.9	434.3	428.9	430.2	422.1	422.1
65°	372.1	373.4	380.2	386.9	386.9	389.6	386.9	388.3	384.2	384.2	378.8
67.5°	326.1	326.1	332.8	339.6	346.3	346.3	346.3	342.3	342.3	338.2	338.2
70°	285.5	284.1	290.9	294.9	299.0	300.3	297.6	296.3	293.6	289.5	288.2
72.5°	235.4	238.1	244.9	247.6	254.3	253.0	259.8	251.6	251.6	244.9	243.5
75°	190.8	193.5	200.2	204.3	208.3	208.3	212.4	208.3	202.9	200.2	198.9
77.5°	151.5	150.2	155.6	162.4	163.7	162.4	165.1	163.7	158.3	158.3	155.6
80°	108.2	112.3	117.7	116.4	121.8	120.4	120.4	117.7	117.7	113.6	116.4
82.5°	71.7	75.8	77.1	75.8	77.1	79.8	81.2	79.8	79.8	77.1	78.5
85°	37.9	37.9	40.6	41.9	40.6	40.6	41.9	46.0	43.3	40.6	43.3
87.5°	12.2	10.8	10.8	12.2	10.8	10.8	12.2	12.2	13.5	13.5	13.5
90°	32.6	33.7	32.5	33.7	34.8	33.7	34.8	33.7	32.5	33.7	32.6
92.5°	73.8	69.7	67.3	62.7	63.9	61.5	63.9	62.7	67.3	69.7	73.8
95°	200.9	180.0	157.9	147.5	139.3	134.7	139.3	147.5	157.9	180.0	200.9
97.5°	505.1	438.9	361.1	317.0	289.1	276.4	289.1	317.0	361.1	438.9	505.1
100°	1056.6	974.2	856.9	772.2	726.9	728.1	726.9	772.2	856.9	974.2	1056.6
102.5°	1414.9	1370.2	1285.4	1222.7	1186.7	1153.0	1186.7	1222.7	1285.4	1370.2	1414.9
105°	1632.6	1617.5	1564.1	1520.0	1482.8	1477.0	1482.8	1520.0	1564.1	1617.5	1632.6
107.5°	1728.4	1744.1	1737.1	1716.2	1701.1	1688.3	1701.1	1716.2	1737.1	1744.1	1728.4
110°	1731.4	1772.0	1804.5	1813.8	1811.4	1809.1	1811.4	1813.8	1804.5	1772.0	1731.4

TEST NUMBER: P1011075

CATALOG NUMBER: S123DIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1665.7	1720.9	1787.0	1820.7	1832.3	1833.5	1832.3	1820.7	1787.0	1720.9	1665.7
115°	1565.8	1629.1	1716.2	1767.3	1790.5	1796.3	1790.5	1767.3	1716.2	1629.1	1565.8
117.5°	1459.0	1524.6	1615.2	1672.1	1706.9	1715.1	1706.9	1672.1	1615.2	1524.6	1459.0
120°	1358.0	1416.6	1508.4	1573.4	1601.3	1608.2	1601.3	1573.4	1508.4	1416.6	1358.0
122.5°	1278.4	1331.9	1410.8	1467.7	1499.1	1508.4	1499.1	1467.7	1410.8	1331.9	1278.4
125°	1207.6	1254.1	1328.4	1379.5	1408.5	1416.6	1408.5	1379.5	1328.4	1254.1	1207.6
127.5°	1149.6	1192.5	1259.9	1304.0	1330.7	1337.7	1330.7	1304.0	1259.9	1192.5	1149.6
130°	1096.2	1135.6	1197.2	1239.0	1263.4	1272.6	1263.4	1239.0	1197.2	1135.6	1096.2
132.5°	1046.2	1083.4	1140.3	1182.1	1203.0	1208.8	1203.0	1182.1	1140.3	1083.4	1046.2
135°	994.6	1027.6	1084.5	1119.4	1140.3	1148.4	1140.3	1119.4	1084.5	1027.6	994.6
137.5°	945.8	975.4	1024.2	1060.2	1077.6	1084.5	1077.6	1060.2	1024.2	975.4	945.8
140°	898.2	923.1	967.3	999.8	1018.3	1017.2	1018.3	999.8	967.3	923.1	898.2
142.5°	854.6	875.5	911.5	939.4	955.6	954.5	955.6	939.4	911.5	875.5	854.6
145°	815.8	832.6	861.6	886.0	895.3	897.6	895.3	886.0	861.6	832.6	815.8
147.5°	785.5	797.7	820.9	838.4	847.7	848.8	847.7	838.4	820.9	797.7	785.5
150°	758.8	769.9	787.3	800.0	807.0	807.0	807.0	800.0	787.3	769.9	758.8
152.5°	735.6	744.3	757.1	768.7	772.2	772.2	772.2	768.7	757.1	744.3	735.6
155°	714.2	721.1	731.5	740.8	743.2	744.3	743.2	740.8	731.5	721.1	714.2
157.5°	693.2	699.0	708.3	715.3	717.6	717.6	717.6	715.3	708.3	699.0	693.2
160°	674.0	678.1	686.3	693.2	693.2	692.1	693.2	693.2	686.3	678.1	674.0
162.5°	656.0	659.5	664.2	670.0	670.0	668.8	670.0	670.0	664.2	659.5	656.0
165°	638.1	641.0	645.6	650.3	649.1	649.1	649.1	650.3	645.6	641.0	638.1
167.5°	622.4	624.7	627.0	630.5	629.4	629.4	629.4	630.5	627.0	624.7	622.4
170°	608.4	609.6	610.8	613.1	611.9	611.9	611.9	613.1	610.8	609.6	608.4
172.5°	596.2	596.8	596.8	599.2	596.8	595.7	596.8	599.2	596.8	596.8	596.2
175°	585.2	585.2	585.2	586.4	585.2	584.1	585.2	586.4	585.2	585.2	585.2
177.5°	578.3	578.3	577.1	578.3	575.9	575.9	575.9	578.3	577.1	578.3	578.3
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1011075

CATALOG NUMBER: S123DIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2
2.5°	1325.9	1328.6	1329.9	1324.5	1320.5	1327.2	1336.7	1343.5	1348.9	1355.6	1359.7
5°	1247.4	1256.9	1256.9	1259.6	1263.6	1270.4	1288.0	1300.2	1311.0	1319.1	1325.9
7.5°	1181.1	1187.9	1191.9	1198.7	1205.5	1214.9	1235.2	1252.8	1269.0	1278.5	1289.3
10°	1121.6	1127.0	1133.7	1137.8	1150.0	1163.5	1189.2	1204.1	1223.0	1237.9	1251.5
12.5°	1064.7	1083.7	1087.7	1086.4	1097.2	1112.1	1137.8	1160.8	1181.1	1196.0	1210.9
15°	1024.2	1030.9	1039.0	1037.7	1060.7	1064.7	1086.4	1113.5	1140.5	1150.0	1163.5
17.5°	979.5	990.3	998.5	1002.5	1009.3	1024.2	1044.5	1064.7	1099.9	1101.3	1136.5
20°	944.3	955.2	960.6	966.0	970.0	987.6	1005.2	1028.2	1056.6	1071.5	1090.5
22.5°	921.3	926.8	930.8	934.9	940.3	949.8	971.4	997.1	1016.0	1032.3	1044.5
25°	894.3	899.7	905.1	907.8	911.9	917.3	933.5	953.8	980.9	991.7	1003.9
27.5°	875.3	875.3	878.0	878.0	883.5	888.9	901.0	920.0	941.6	955.2	971.4
30°	855.0	853.7	855.0	853.7	852.3	860.5	871.3	887.5	902.4	918.6	929.5
32.5°	834.8	833.4	833.4	834.8	829.3	833.4	838.8	853.7	869.9	878.0	890.2
35°	813.1	810.4	810.4	810.4	807.7	805.0	810.4	823.9	834.8	845.6	855.0
37.5°	791.5	787.4	787.4	784.7	782.0	777.9	777.9	788.8	803.6	807.7	819.9
40°	761.7	761.7	759.0	757.6	754.9	752.2	748.2	757.6	771.2	775.2	784.7
42.5°	731.9	727.9	726.5	726.5	726.5	722.5	719.8	726.5	734.6	741.4	746.8
45°	698.1	695.4	696.8	695.4	692.7	691.3	690.0	692.7	702.2	704.9	711.6
47.5°	661.6	660.2	660.2	658.9	657.5	658.9	653.5	660.2	662.9	665.6	671.0
50°	623.7	622.3	621.0	619.6	619.6	621.0	619.6	619.6	625.0	627.8	633.2
52.5°	585.8	581.8	581.8	580.4	580.4	577.7	580.4	581.8	584.5	587.2	589.9
55°	545.2	545.2	541.2	541.2	538.5	538.5	539.8	538.5	543.9	546.6	546.6
57.5°	506.0	500.6	501.9	499.2	496.5	495.2	495.2	497.9	500.6	500.6	503.3
60°	464.1	458.6	457.3	451.9	454.6	450.5	451.9	451.9	457.3	454.6	457.3
62.5°	422.1	415.3	411.3	408.6	408.6	409.9	407.2	405.9	408.6	411.3	416.7
65°	377.5	373.4	369.3	365.3	365.3	363.9	366.6	362.6	361.2	362.6	365.3
67.5°	331.5	327.4	323.3	319.3	320.6	316.6	313.9	317.9	315.2	316.6	319.3
70°	286.8	284.1	276.0	273.3	271.9	273.3	271.9	269.2	273.3	271.9	273.3
72.5°	242.2	239.5	235.4	228.6	228.6	227.3	225.9	225.9	224.6	224.6	224.6
75°	198.9	193.5	189.4	188.1	185.4	184.0	182.6	179.9	181.3	182.6	179.9
77.5°	154.2	147.5	146.1	146.1	142.1	142.1	143.4	142.1	140.7	140.7	140.7
80°	113.6	108.2	108.2	105.5	102.8	102.8	102.8	102.8	101.5	100.1	101.5
82.5°	73.1	71.7	70.4	70.4	73.1	67.6	70.4	69.0	67.6	67.6	66.3
85°	40.6	41.9	40.6	41.9	39.2	40.6	40.6	40.6	39.2	40.6	37.9
87.5°	14.9	14.9	14.9	16.2	16.2	16.2	16.2	16.2	17.6	16.2	16.2
90°	31.4	30.2	29.0	27.9	29.0	25.5	22.1	18.6	15.1	14.0	12.8
92.5°	77.8	89.4	115.0	161.4	216.0	239.2	178.8	117.3	80.1	69.6	59.2
95°	221.8	283.3	418.0	558.5	688.6	613.1	422.7	249.7	151.0	128.4	105.7
97.5°	571.3	724.6	960.3	1095.0	1059.0	790.8	470.3	269.4	171.9	146.9	121.9
100°	1139.1	1275.0	1369.0	1328.4	1099.6	743.2	437.8	265.9	184.6	162.0	139.3
102.5°	1459.6	1524.6	1504.9	1340.0	1024.2	673.5	409.9	270.6	199.7	179.4	159.1
105°	1647.7	1625.6	1509.5	1266.8	933.6	618.9	399.4	279.8	217.1	199.1	181.1
107.5°	1712.7	1622.2	1439.9	1162.3	853.5	579.4	397.1	294.9	239.2	222.4	205.5
110°	1690.7	1544.4	1330.7	1064.8	787.3	558.5	402.9	314.7	262.4	246.2	229.9

TEST NUMBER: P1011075

CATALOG NUMBER: S123DIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1610.5	1442.2	1222.7	980.0	743.2	546.9	414.5	334.4	286.8	271.2	255.5
115°	1502.6	1331.9	1129.8	915.0	714.1	545.8	427.3	356.5	312.4	296.7	281.0
117.5°	1393.4	1236.6	1057.8	872.0	694.4	546.9	443.6	379.7	335.6	321.0	306.5
120°	1299.4	1160.0	1003.3	839.5	681.6	551.6	462.1	401.8	360.0	345.4	330.9
122.5°	1225.0	1098.5	960.3	812.8	673.5	559.7	479.6	425.0	384.3	368.6	353.0
125°	1161.2	1049.7	923.1	790.8	666.5	567.8	498.1	447.1	406.4	390.8	375.1
127.5°	1106.6	1004.4	889.5	769.9	663.0	577.1	513.2	466.8	427.3	411.6	396.0
130°	1056.7	962.6	858.1	753.6	659.5	586.4	528.3	484.2	445.9	430.2	414.5
132.5°	1009.1	923.1	829.1	738.5	658.4	593.4	542.3	499.3	462.1	447.0	432.0
135°	961.5	886.0	803.5	725.7	657.2	600.3	553.9	514.4	478.4	462.8	447.1
137.5°	916.2	848.8	779.1	714.1	654.9	605.0	563.2	524.9	490.0	475.5	461.0
140°	873.2	817.5	758.2	703.7	653.7	609.6	570.1	535.3	501.6	487.1	472.6
142.5°	833.7	787.3	738.5	694.4	651.4	613.1	577.1	543.4	510.9	497.6	484.2
145°	798.9	761.7	723.4	686.3	649.1	614.3	581.7	550.4	520.2	506.8	493.5
147.5°	773.3	742.0	710.6	678.1	645.6	614.3	585.2	556.2	528.3	516.7	505.1
150°	747.8	723.4	696.7	670.0	641.0	614.3	586.4	562.0	535.3	524.8	514.4
152.5°	726.9	706.0	683.9	660.7	635.2	610.8	588.7	565.5	543.4	533.6	523.7
155°	707.2	689.7	671.2	651.4	628.2	608.5	588.7	570.1	550.4	542.2	534.1
157.5°	687.4	673.5	657.2	641.0	622.4	605.0	589.9	572.5	556.2	549.8	543.4
160°	670.0	658.4	645.6	630.5	615.4	602.6	589.9	575.9	562.0	556.2	550.4
162.5°	652.6	642.1	631.7	620.1	608.5	598.0	588.7	577.1	565.5	560.8	556.2
165°	635.2	627.0	620.1	610.8	601.5	593.4	586.4	578.3	569.0	564.9	560.8
167.5°	620.1	615.4	609.6	601.5	594.5	588.7	585.2	578.3	571.3	568.4	565.5
170°	607.3	602.6	599.2	593.4	587.6	584.1	581.7	577.1	571.3	570.2	569.0
172.5°	595.7	592.2	589.9	585.2	581.7	580.6	580.6	577.1	572.5	571.9	571.3
175°	585.2	582.9	581.7	579.4	577.1	577.1	578.3	575.9	573.6	573.0	572.5
177.5°	578.3	577.1	575.9	574.8	573.6	574.8	577.1	574.8	573.6	573.6	573.6
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1011075

CATALOG NUMBER: S123DIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1396.2	1396.2	1396.2	1396.2
2.5°	1366.5	1370.5	1384.0	1400.3
5°	1339.4	1350.2	1369.2	1394.9
7.5°	1309.6	1325.9	1352.9	1385.4
10°	1275.8	1298.8	1332.6	1373.2
12.5°	1239.3	1269.0	1312.3	1354.3
15°	1216.3	1246.0	1285.3	1331.3
17.5°	1171.6	1206.8	1247.4	1312.3
20°	1125.6	1164.9	1217.6	1282.6
22.5°	1090.5	1132.4	1182.5	1251.5
25°	1048.5	1091.8	1145.9	1217.6
27.5°	1003.9	1047.2	1108.0	1183.8
30°	970.0	1012.0	1070.2	1151.3
32.5°	929.5	970.0	1030.9	1116.2
35°	883.5	929.5	987.6	1074.2
37.5°	848.3	890.2	951.1	1033.6
40°	810.4	846.9	906.5	987.6
42.5°	769.8	810.4	861.8	943.0
45°	731.9	761.7	814.5	891.6
47.5°	691.3	725.2	765.8	825.3
50°	648.0	676.5	721.1	761.7
52.5°	606.1	629.1	667.0	698.1
55°	561.5	584.5	612.9	631.8
57.5°	519.5	535.8	554.7	566.9
60°	468.1	484.3	496.5	508.7
62.5°	422.1	434.3	441.1	447.8
65°	374.8	381.5	385.6	391.0
67.5°	323.3	330.1	331.5	339.6
70°	276.0	277.3	280.1	284.1
72.5°	231.3	234.1	232.7	235.4
75°	185.4	188.1	185.4	188.1
77.5°	140.7	143.4	143.4	147.5
80°	101.5	102.8	104.2	104.2
82.5°	66.3	70.4	67.6	69.0
85°	37.9	39.2	39.2	40.6
87.5°	17.6	18.9	17.6	20.3
90°	10.5	7.0	4.6	2.3
92.5°	47.6	37.2	25.5	17.4
95°	75.5	55.7	43.0	39.5
97.5°	91.7	74.3	63.9	62.7
100°	111.5	95.2	87.1	85.9
102.5°	134.7	119.6	112.6	110.3
105°	159.1	145.1	138.2	134.7
107.5°	184.6	170.7	163.7	160.2
110°	210.2	197.4	191.6	188.1

TEST NUMBER: P1011075

CATALOG NUMBER: S123DIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	235.7	222.9	217.1	213.7
115°	261.3	249.7	242.7	238.0
117.5°	284.5	274.0	268.2	262.4
120°	308.9	297.3	291.5	288.0
122.5°	332.1	319.3	313.5	310.0
125°	353.0	340.2	333.3	330.9
127.5°	371.6	358.8	350.7	347.2
130°	390.2	376.2	365.8	362.3
132.5°	407.6	390.2	378.5	373.9
135°	422.7	405.2	392.5	387.8
137.5°	436.6	418.0	405.2	400.6
140°	449.4	430.8	419.2	413.4
142.5°	461.0	444.7	432.0	427.3
145°	473.8	456.3	445.9	442.4
147.5°	485.4	470.3	459.8	457.5
150°	498.1	483.0	473.8	472.6
152.5°	509.8	497.0	487.7	487.7
155°	521.4	509.8	502.8	502.8
157.5°	531.8	521.4	515.6	514.4
160°	542.3	533.0	528.3	528.3
162.5°	549.2	542.3	538.8	538.8
165°	556.2	550.4	548.1	549.2
167.5°	562.0	557.4	556.2	557.4
170°	566.7	563.2	562.0	564.3
172.5°	570.1	567.8	567.8	569.0
175°	572.5	570.1	571.3	572.5
177.5°	573.6	572.5	573.6	574.8
180°	573.6	573.6	573.6	573.6

(END OF REPORT)