

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011240

Luminaire Tested: S123DIP-B1165D1025UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011240
REPORT IS A COMBINATION OF REPORTS P989321 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1165D1025UB27-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8508.0 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011240

CATALOG NUMBER: S123DIP-B1165D1025UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1011240

CATALOG NUMBER: S123DIP-B1165D1025UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63
1	100	95	92	88	93	89	86	83	77	75	72	66	64	63	56	55	54
2	91	84	78	73	85	78	73	68	68	64	60	58	55	53	50	48	46
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	41	39
4	76	66	58	52	71	61	54	49	54	48	44	46	42	39	40	37	34
5	70	59	50	44	65	55	48	42	48	42	38	42	37	34	36	32	30
6	65	53	45	39	60	49	42	37	43	38	33	38	33	30	33	29	26
7	60	48	40	34	56	45	38	32	39	34	29	34	30	26	30	26	23
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	27	24	21
9	52	40	32	27	48	37	30	26	33	27	23	29	24	21	25	22	19
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17350	17350	17350	17350
5°	17361	19991	17412	14920
10°	17252	24191	17269	13029
15°	17013	28690	17151	11728
20°	16808	33032	16843	10792
25°	16503	33864	16540	10303
30°	16286	27978	16286	9983
35°	16016	18711	15916	9701
40°	15692	13507	15498	9267
45°	15286	10699	14845	8729
50°	14300	9087	13791	8201
55°	13216	7984	12678	7612
60°	12119	6952	11473	6992
65°	10912	5953	10383	6167
70°	9659	4942	9014	5198
75°	8258	3727	7726	4012
80°	6531	2488	6021	2636
85°	4505	1141	3602	1040

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 27982 cd/sqm

TEST NUMBER: P1011240

CATALOG NUMBER: S123DIP-B1165D1025UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.5	1.9
10°-20°	509.2	6.0
20°-30°	856.7	10.1
30°-40°	968.2	11.4
40°-50°	867.2	10.2
50°-60°	700.0	8.2
60°-70°	487.8	5.7
70°-80°	256.0	3.0
80°-90°	64.1	0.8
90°-100°	262.6	3.1
100°-110°	768.8	9.0
110°-120°	750.8	8.8
120°-130°	597.9	7.0
130°-140°	471.8	5.5
140°-150°	351.9	4.1
150°-160°	245.4	2.9
160°-170°	144.1	1.7
170°-180°	46.9	0.6
0°-30°	1524.4	17.9
0°-40°	2492.6	29.3
0°-60°	4059.8	47.7
0°-90°	4867.7	57.2
90°-120°	1782.3	20.9
90°-150°	3203.9	37.7
90°-180°	3640.0	42.8
0°-180°	8508.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1612	1612	1612	1612	1612	
5°	1610	1915	1615	1429	1610	153
15°	1537	2850	1549	1165	1537	434
25°	1406	3383	1409	1029	1406	648
35°	1240	1823	1232	945	1240	776
45°	1029	984	1000	803	1029	787
55°	729	668	700	637	729	653
65°	451	434	430	450	451	450
75°	217	223	203	240	217	233
85°	47	52	38	47	47	54
90°	2	28	2	28	2	6
95°	33	114	33	114	33	35
105°	114	1246	114	1246	114	121
115°	201	1516	201	1516	201	199
125°	279	1195	279	1195	279	248
135°	327	969	327	969	327	253
145°	373	757	373	757	373	234
155°	424	628	424	628	424	195
165°	463	548	463	548	463	131
175°	483	493	483	493	483	46
180°	484	484	484	484	484	

TEST NUMBER: P1011240

CATALOG NUMBER: S123DIP-B1165D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9
2.5°	1616.6	1629.1	1635.3	1644.7	1654.1	1668.1	1672.8	1680.6	1677.5	1683.8	1686.9
5°	1610.3	1632.2	1651.0	1674.4	1696.3	1711.9	1727.5	1752.5	1771.2	1774.3	1788.4
7.5°	1599.4	1630.7	1663.5	1696.3	1738.4	1763.4	1791.5	1825.9	1854.0	1899.3	1916.5
10°	1585.4	1629.1	1675.9	1721.2	1779.0	1818.1	1852.4	1910.2	1968.0	2014.9	2058.6
12.5°	1563.5	1618.2	1679.1	1746.2	1821.2	1866.5	1913.4	1989.9	2077.4	2149.2	2196.1
15°	1536.9	1605.7	1683.8	1755.6	1838.4	1922.7	1972.7	2058.6	2183.6	2250.7	2371.0
17.5°	1515.1	1585.4	1663.5	1775.9	1888.4	1972.7	2008.6	2166.4	2252.3	2364.8	2500.6
20°	1480.7	1569.7	1669.7	1782.2	1927.4	1979.0	2052.4	2211.7	2317.9	2464.7	2631.8
22.5°	1444.8	1540.1	1660.3	1777.5	1939.9	1994.6	2094.5	2221.1	2389.7	2535.0	2719.3
25°	1405.7	1508.8	1630.7	1769.7	1929.0	2008.6	2102.4	2258.5	2441.3	2624.0	2794.3
27.5°	1366.7	1479.1	1605.7	1744.7	1899.3	1993.0	2086.7	2249.2	2483.5	2681.8	2898.9
30°	1329.2	1441.7	1568.2	1710.3	1872.8	1963.3	2052.4	2255.4	2516.3	2739.6	2958.3
32.5°	1288.6	1404.2	1536.9	1655.6	1819.6	1916.5	2016.4	2255.4	2536.6	2774.0	2973.9
35°	1240.2	1358.9	1472.9	1591.6	1754.0	1861.8	1974.3	2239.8	2555.3	2784.9	2908.3
37.5°	1193.3	1298.0	1396.4	1511.9	1682.2	1797.8	1927.4	2221.1	2545.9	2738.1	2772.4
40°	1140.2	1244.9	1324.5	1432.3	1611.9	1746.2	1877.4	2196.1	2505.3	2627.2	2527.2
42.5°	1088.7	1171.4	1240.2	1344.8	1540.1	1671.3	1813.4	2150.8	2425.7	2450.7	2225.7
45°	1029.3	1088.7	1149.6	1268.3	1462.0	1596.3	1754.0	2085.2	2297.6	2225.7	1941.5
47.5°	952.8	1005.9	1073.0	1182.4	1379.2	1518.2	1668.1	2000.8	2111.7	1961.8	1651.0
50°	879.4	924.7	987.1	1093.3	1291.7	1427.6	1586.9	1868.1	1922.7	1686.9	1422.9
52.5°	806.0	840.3	901.2	1007.4	1205.8	1337.0	1482.3	1732.2	1700.9	1447.9	1213.6
55°	729.4	759.1	816.9	921.5	1105.8	1230.8	1369.8	1565.1	1483.8	1243.3	1055.9
57.5°	654.4	685.7	745.0	832.5	1005.9	1127.7	1238.6	1391.7	1269.8	1077.7	912.2
60°	587.3	613.8	659.1	745.0	902.8	1001.2	1102.7	1207.4	1105.8	920.0	793.5
62.5°	517.0	542.0	584.2	662.3	798.1	885.6	966.8	1052.7	940.3	804.4	691.9
65°	451.4	471.7	510.8	582.6	693.5	765.3	830.9	890.3	799.7	674.8	590.4
67.5°	392.0	409.2	442.0	506.1	599.8	651.3	704.4	754.4	677.9	577.9	506.1
70°	328.0	342.1	371.7	418.6	493.6	546.7	585.7	623.2	554.5	474.8	426.4
72.5°	271.8	285.8	304.6	353.0	404.5	437.3	479.5	499.8	460.8	395.2	346.7
75°	217.1	228.0	245.2	276.5	324.9	346.7	373.3	388.9	353.0	309.3	279.6
77.5°	170.3	174.9	187.4	209.3	242.1	267.1	287.4	296.8	271.8	243.7	218.7
80°	120.3	126.5	135.9	154.6	179.6	187.4	199.9	210.9	195.2	170.3	154.6
82.5°	79.7	87.5	92.2	100.0	115.6	125.0	128.1	137.4	123.4	114.0	107.8
85°	46.9	50.0	51.5	56.2	64.0	68.7	73.4	75.0	71.8	70.3	64.0
87.5°	23.4	23.4	23.4	26.6	28.1	31.2	32.8	32.8	32.8	31.2	29.7
90°	2.0	3.9	5.9	8.8	10.8	11.8	12.7	15.7	18.6	21.6	24.5
92.5°	14.7	21.6	31.3	40.2	50.0	58.8	67.6	98.9	150.9	201.8	182.2
95°	33.3	36.2	47.0	63.7	89.1	108.2	127.4	210.6	356.6	517.3	580.9
97.5°	52.9	53.9	62.7	77.4	102.9	124.0	145.0	227.3	396.8	667.1	893.4
100°	72.5	73.5	80.3	94.0	117.6	136.7	155.8	224.3	369.3	627.0	927.7
102.5°	93.1	95.0	100.9	113.6	134.2	151.4	168.5	228.3	345.8	568.2	864.1
105°	113.6	116.6	122.5	134.2	152.8	168.0	183.2	236.1	337.0	522.2	787.6
107.5°	135.2	138.1	144.0	155.8	173.4	187.6	201.8	248.8	335.0	488.8	720.0
110°	158.7	161.6	166.5	177.3	194.0	207.7	221.4	265.5	339.9	471.2	664.2

TEST NUMBER: P1011240

CATALOG NUMBER: S123DIP-B1165D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	180.3	183.2	188.1	198.9	215.5	228.8	242.0	282.1	349.7	461.4	627.0
115°	200.8	204.7	210.6	220.4	237.1	250.3	263.5	300.8	360.5	460.4	602.5
117.5°	221.4	226.3	231.2	240.0	258.6	270.8	283.1	320.3	374.2	461.4	585.8
120°	243.0	245.9	250.8	260.6	279.2	291.4	303.7	339.0	389.9	465.3	575.1
122.5°	261.6	264.5	269.4	280.2	297.8	311.0	324.3	358.6	404.6	472.2	568.2
125°	279.2	281.2	287.0	297.8	316.4	329.6	342.9	377.2	420.3	479.1	562.3
127.5°	292.9	295.9	302.7	313.5	334.1	347.3	360.5	393.8	433.0	486.9	559.4
130°	305.7	308.6	317.4	329.2	349.7	363.0	376.2	408.5	445.7	494.7	556.4
132.5°	315.4	319.4	329.2	343.9	364.4	377.2	389.9	421.3	457.5	500.6	555.5
135°	327.2	331.1	341.9	356.6	377.2	390.4	403.6	434.0	467.3	506.5	554.5
137.5°	338.0	341.9	352.7	368.4	388.9	401.2	413.4	442.8	475.1	510.4	552.5
140°	348.8	353.7	363.5	379.1	398.7	411.0	423.2	451.6	481.0	514.3	551.5
142.5°	360.5	364.4	375.2	388.9	408.5	419.8	431.0	458.5	486.9	517.3	549.6
145°	373.2	376.2	385.0	399.7	416.4	427.6	438.9	464.4	490.8	518.2	547.6
147.5°	386.0	387.9	396.8	409.5	426.2	436.0	445.7	469.3	493.7	518.2	544.7
150°	398.7	399.7	407.5	420.3	434.0	442.8	451.6	474.2	494.7	518.2	540.8
152.5°	411.5	411.5	419.3	430.1	441.8	450.2	458.5	477.1	496.7	515.3	535.9
155°	424.2	424.2	430.1	439.9	450.6	457.5	464.4	481.0	496.7	513.3	530.0
157.5°	434.0	435.0	439.9	448.7	458.5	463.9	469.3	483.0	497.7	510.4	525.1
160°	445.7	445.7	449.7	457.5	464.4	469.3	474.2	485.9	497.7	508.4	519.2
162.5°	454.6	454.6	457.5	463.4	469.3	473.2	477.1	486.9	496.7	504.5	513.3
165°	463.4	462.4	464.4	469.3	473.2	476.6	480.0	487.9	494.7	500.6	507.5
167.5°	470.2	469.3	470.2	474.2	477.1	479.6	482.0	487.9	493.7	496.7	501.6
170°	476.1	474.2	475.1	478.1	480.0	481.0	482.0	486.9	490.8	492.8	495.7
172.5°	480.0	479.1	479.1	481.0	482.0	482.5	483.0	486.9	489.8	489.8	490.8
175°	483.0	482.0	481.0	483.0	483.0	483.4	483.9	485.9	487.9	486.9	486.9
177.5°	484.9	483.9	483.0	483.9	483.9	483.9	483.9	484.9	486.9	484.9	483.9
180°	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9

TEST NUMBER: P1011240

CATALOG NUMBER: S123DIP-B1165D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9
2.5°	1697.8	1700.9	1711.9	1719.7	1735.3	1733.7	1733.7	1732.2	1727.5	1735.3	1740.0
5°	1816.5	1843.1	1846.2	1880.6	1882.1	1896.2	1905.6	1897.7	1916.5	1914.9	1900.9
7.5°	1963.3	1999.3	2016.4	2049.2	2086.7	2077.4	2113.3	2119.5	2116.4	2132.0	2143.0
10°	2124.2	2186.7	2230.4	2291.3	2307.0	2316.3	2339.8	2360.1	2400.7	2369.4	2389.7
12.5°	2308.5	2353.8	2411.6	2508.5	2556.9	2588.1	2599.0	2613.1	2641.2	2624.0	2625.6
15°	2463.2	2524.1	2622.5	2742.7	2756.8	2795.8	2786.5	2870.8	2911.4	2850.5	2884.9
17.5°	2624.0	2705.3	2822.4	2927.1	2986.4	3013.0	3037.9	3119.2	3116.0	3106.7	3114.5
20°	2727.1	2859.9	3005.1	3144.2	3161.3	3181.6	3248.8	3283.2	3276.9	3303.5	3320.7
22.5°	2872.4	3013.0	3167.6	3259.7	3298.8	3322.2	3375.3	3397.2	3406.6	3412.8	3401.9
25°	2994.2	3144.2	3258.2	3339.4	3362.8	3375.3	3392.5	3398.8	3394.1	3383.1	3392.5
27.5°	3077.0	3197.3	3275.4	3312.8	3300.4	3280.0	3247.2	3225.4	3177.0	3153.5	3181.6
30°	3111.4	3164.5	3187.9	3125.4	3062.9	3013.0	2950.5	2834.9	2744.3	2770.9	2734.9
32.5°	3056.7	3022.3	2909.9	2749.0	2700.6	2619.4	2442.9	2307.0	2311.7	2239.8	2269.5
35°	2895.8	2739.6	2527.2	2283.5	2219.5	2175.8	1982.1	1952.4	1889.9	1822.8	1841.5
37.5°	2611.5	2383.5	2125.8	1946.2	1850.9	1755.6	1646.3	1580.7	1543.2	1515.1	1536.9
40°	2264.8	1986.8	1774.3	1613.5	1532.3	1471.3	1396.4	1330.8	1288.6	1283.9	1291.7
42.5°	1924.3	1690.0	1494.8	1341.7	1315.1	1243.3	1194.9	1143.3	1130.8	1110.5	1121.5
45°	1629.1	1438.5	1277.7	1152.7	1121.5	1102.7	1043.4	1010.6	996.5	984.0	1002.8
47.5°	1415.1	1215.2	1098.0	1023.1	991.8	960.6	927.8	905.9	895.0	896.5	895.0
50°	1208.9	1062.1	959.0	901.2	882.5	860.6	834.1	820.0	815.3	801.3	812.2
52.5°	1040.2	934.0	862.2	807.5	793.5	777.8	756.0	748.2	737.2	734.1	734.1
55°	904.4	821.6	763.8	727.9	710.7	698.2	685.7	676.3	668.5	668.5	668.5
57.5°	798.1	726.3	684.1	652.9	646.6	634.1	620.1	620.1	609.2	607.6	612.3
60°	707.6	643.5	610.7	584.2	574.8	571.7	557.6	557.6	554.5	546.7	552.9
62.5°	615.4	568.5	540.4	520.1	510.8	510.8	499.8	492.0	492.0	493.6	490.4
65°	531.1	496.7	471.7	456.1	451.4	445.1	443.6	437.3	432.7	434.2	432.7
67.5°	456.1	429.5	412.3	399.9	392.0	388.9	384.2	384.2	381.1	382.7	374.9
70°	388.9	362.4	348.3	335.8	332.7	332.7	326.4	328.0	324.9	329.6	326.4
72.5°	320.2	299.9	289.0	284.3	281.1	279.6	276.5	273.3	271.8	274.9	273.3
75°	259.3	242.1	234.3	231.2	228.0	228.0	226.5	224.9	223.4	223.4	223.4
77.5°	201.5	190.6	181.2	184.3	179.6	181.2	176.5	176.5	178.1	176.5	176.5
80°	148.4	140.6	140.6	137.4	131.2	134.3	134.3	129.6	128.1	131.2	126.5
82.5°	98.4	96.8	93.7	92.2	89.0	90.6	89.0	87.5	85.9	89.0	85.9
85°	57.8	57.8	56.2	53.1	56.2	54.7	53.1	53.1	51.5	51.5	51.5
87.5°	29.7	26.6	26.6	25.0	26.6	23.4	25.0	23.4	21.9	23.4	21.9
90°	23.5	24.5	25.5	26.5	27.4	28.4	27.4	28.4	29.4	28.4	29.4
92.5°	136.2	97.0	75.4	65.6	62.2	58.8	56.8	52.9	53.9	51.9	53.9
95°	471.2	352.7	239.0	187.1	169.4	151.8	133.2	124.4	117.6	113.6	117.6
97.5°	923.8	810.2	611.3	482.0	426.2	370.3	304.7	267.4	243.9	233.2	243.9
100°	1120.7	1155.0	1075.7	961.0	891.4	821.9	723.0	651.5	613.3	614.2	613.3
102.5°	1130.5	1269.6	1286.3	1231.4	1193.7	1156.0	1084.5	1031.6	1001.2	972.8	1001.2
105°	1068.8	1273.6	1371.5	1390.1	1377.4	1364.7	1319.6	1282.4	1251.0	1246.1	1251.0
107.5°	980.6	1214.8	1368.6	1445.0	1458.2	1471.4	1465.6	1447.9	1435.2	1424.4	1435.2
110°	898.3	1122.7	1302.9	1426.4	1460.7	1495.0	1522.4	1530.2	1528.3	1526.3	1528.3

TEST NUMBER: P1011240

CATALOG NUMBER: S123DIP-B1165D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	826.8	1031.6	1216.7	1358.8	1405.3	1451.8	1507.7	1536.1	1545.9	1546.9	1545.9
115°	772.0	953.2	1123.7	1267.7	1321.1	1374.5	1447.9	1491.0	1510.6	1515.5	1510.6
117.5°	735.7	892.5	1043.3	1175.6	1230.9	1286.3	1362.7	1410.7	1440.1	1447.0	1440.1
120°	708.3	846.4	978.7	1096.2	1145.7	1195.2	1272.6	1327.4	1350.9	1356.8	1350.9
122.5°	685.8	810.2	926.8	1033.5	1078.6	1123.7	1190.3	1238.3	1264.7	1272.6	1264.7
125°	667.1	778.8	885.6	979.7	1018.8	1058.0	1120.7	1163.8	1188.3	1195.2	1188.3
127.5°	649.5	750.4	847.4	933.6	969.8	1006.1	1062.9	1100.2	1122.7	1128.6	1122.7
130°	635.8	724.0	812.1	891.5	924.8	958.1	1010.0	1045.3	1065.9	1073.7	1065.9
132.5°	623.1	699.5	778.8	851.3	882.6	914.0	962.0	997.3	1014.9	1019.8	1014.9
135°	612.3	677.9	747.5	811.2	839.1	867.0	915.0	944.4	962.0	968.9	962.0
137.5°	602.5	657.3	716.1	772.9	797.9	822.9	864.1	894.4	909.1	915.0	909.1
140°	593.7	639.7	689.7	736.7	757.8	778.8	816.1	843.5	859.2	858.2	859.2
142.5°	585.8	623.1	664.2	703.4	721.0	738.7	769.0	792.5	806.3	805.3	806.3
145°	579.0	610.3	642.7	674.0	688.2	702.4	726.9	747.5	755.3	757.3	755.3
147.5°	572.1	599.5	626.0	652.5	662.8	673.0	692.6	707.3	715.1	716.1	715.1
150°	565.3	587.8	610.3	630.9	640.2	649.5	664.2	675.0	680.9	680.9	680.9
152.5°	557.4	577.0	595.6	613.3	620.6	628.0	638.7	648.5	651.5	651.5	651.5
155°	549.6	566.2	581.9	596.6	602.5	608.4	617.2	625.0	627.0	628.0	627.0
157.5°	540.8	554.5	568.2	580.0	584.9	589.8	597.6	603.5	605.4	605.4	605.4
160°	532.0	544.7	555.5	565.3	568.7	572.1	579.0	584.9	584.9	583.9	584.9
162.5°	523.1	532.9	541.7	550.6	553.5	556.4	560.4	565.3	565.3	564.3	565.3
165°	515.3	523.1	529.0	535.9	538.3	540.8	544.7	548.6	547.6	547.6	547.6
167.5°	507.5	514.3	519.2	523.1	525.1	527.1	529.0	532.0	531.0	531.0	531.0
170°	500.6	505.5	508.4	512.4	513.3	514.3	515.3	517.3	516.3	516.3	516.3
172.5°	493.7	497.7	499.6	502.6	503.0	503.5	503.5	505.5	503.5	502.6	503.5
175°	488.8	490.8	491.8	493.7	493.7	493.7	493.7	494.7	493.7	492.8	493.7
177.5°	484.9	485.9	486.9	487.9	487.9	487.9	486.9	487.9	485.9	485.9	485.9
180°	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9

TEST NUMBER: P1011240

CATALOG NUMBER: S123DIP-B1165D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9
2.5°	1727.5	1732.2	1719.7	1716.6	1716.6	1722.8	1718.1	1675.9	1683.8	1674.4	1671.3
5°	1918.0	1908.7	1896.2	1889.9	1882.1	1860.3	1858.7	1810.3	1800.9	1769.7	1755.6
7.5°	2127.3	2119.5	2082.0	2077.4	2074.2	2053.9	2002.4	1950.8	1913.4	1877.4	1843.1
10°	2366.3	2342.9	2325.7	2291.3	2274.2	2246.1	2178.9	2130.5	2066.4	2011.8	1939.9
12.5°	2653.7	2627.2	2569.4	2544.4	2522.5	2444.4	2377.3	2322.6	2197.6	2160.1	2071.1
15°	2864.6	2808.3	2802.1	2747.4	2744.3	2658.4	2530.3	2471.0	2374.1	2236.7	2144.5
17.5°	3092.6	3042.6	3003.6	2938.0	2928.6	2847.4	2753.7	2608.4	2502.2	2371.0	2253.9
20°	3259.7	3233.2	3166.0	3139.5	3084.8	3016.1	2919.2	2739.6	2610.0	2478.8	2335.1
22.5°	3392.5	3366.0	3312.8	3276.9	3245.7	3156.7	3041.1	2888.0	2709.9	2538.1	2389.7
25°	3390.9	3383.1	3361.3	3344.1	3320.7	3255.1	3158.2	3011.4	2813.0	2624.0	2417.9
27.5°	3198.8	3220.7	3258.2	3276.9	3272.2	3262.9	3208.2	3084.8	2906.7	2681.8	2450.7
30°	2799.0	2878.6	2948.9	3042.6	3070.7	3139.5	3170.7	3100.4	2958.3	2749.0	2492.8
32.5°	2321.0	2436.6	2589.7	2641.2	2730.2	2863.0	3011.4	3037.9	2948.9	2788.0	2519.4
35°	1904.0	1999.3	2118.0	2199.2	2278.9	2494.4	2681.8	2844.3	2873.9	2767.7	2513.1
37.5°	1576.0	1643.1	1747.8	1816.5	1889.9	2074.2	2336.6	2547.5	2695.9	2699.0	2496.0
40°	1338.6	1368.2	1458.8	1508.8	1579.1	1738.4	1972.7	2247.6	2464.7	2564.7	2450.7
42.5°	1134.0	1173.0	1248.0	1285.5	1330.8	1469.8	1624.4	1885.2	2153.9	2367.9	2366.3
45°	1012.1	1040.2	1074.6	1105.8	1157.4	1240.2	1416.7	1611.9	1869.6	2111.7	2207.0
47.5°	904.4	930.9	965.3	974.6	1009.0	1087.1	1194.9	1365.1	1605.7	1846.2	2025.8
50°	813.8	835.6	859.1	876.2	891.9	955.9	1037.1	1180.8	1372.9	1605.7	1829.0
52.5°	743.5	759.1	779.4	788.8	802.8	849.7	912.2	1018.4	1176.1	1388.6	1605.7
55°	677.9	688.8	701.3	716.9	723.2	757.5	806.0	896.5	1013.7	1204.2	1410.4
57.5°	617.0	621.6	629.5	638.8	646.6	676.3	718.5	779.4	882.5	1029.3	1224.6
60°	548.2	560.7	565.4	574.8	579.5	602.9	635.7	687.2	766.9	893.4	1040.2
62.5°	490.4	498.3	506.1	510.8	521.7	529.5	556.0	602.9	668.5	762.2	895.0
65°	438.9	442.0	446.7	451.4	454.5	463.9	488.9	520.1	570.1	652.9	756.0
67.5°	379.5	382.7	388.9	390.5	393.6	406.1	420.2	446.7	488.9	551.4	635.7
70°	321.8	326.4	329.6	332.7	337.4	342.1	357.7	379.5	412.3	456.1	521.7
72.5°	271.8	276.5	276.5	279.6	278.0	284.3	299.9	315.5	337.4	373.3	431.1
75°	221.8	221.8	224.9	226.5	228.0	234.3	240.5	253.0	270.2	298.3	334.3
77.5°	174.9	173.4	176.5	176.5	176.5	181.2	187.4	193.7	204.6	224.9	253.0
80°	128.1	128.1	131.2	132.8	129.6	131.2	134.3	140.6	148.4	162.4	178.1
82.5°	84.3	90.6	89.0	90.6	89.0	92.2	93.7	95.3	98.4	104.6	115.6
85°	51.5	51.5	51.5	53.1	51.5	53.1	53.1	53.1	54.7	57.8	62.5
87.5°	21.9	21.9	21.9	23.4	21.9	21.9	23.4	21.9	23.4	23.4	25.0
90°	28.4	27.4	28.4	27.4	26.5	25.5	24.5	23.5	24.5	21.6	18.6
92.5°	52.9	56.8	58.8	62.2	65.6	75.4	97.0	136.2	182.2	201.8	150.9
95°	124.4	133.2	151.8	169.4	187.1	239.0	352.7	471.2	580.9	517.3	356.6
97.5°	267.4	304.7	370.3	426.2	482.0	611.3	810.2	923.8	893.4	667.1	396.8
100°	651.5	723.0	821.9	891.4	961.0	1075.7	1155.0	1120.7	927.7	627.0	369.3
102.5°	1031.6	1084.5	1156.0	1193.7	1231.4	1286.3	1269.6	1130.5	864.1	568.2	345.8
105°	1282.4	1319.6	1364.7	1377.4	1390.1	1371.5	1273.6	1068.8	787.6	522.2	337.0
107.5°	1447.9	1465.6	1471.4	1458.2	1445.0	1368.6	1214.8	980.6	720.0	488.8	335.0
110°	1530.2	1522.4	1495.0	1460.7	1426.4	1302.9	1122.7	898.3	664.2	471.2	339.9

TEST NUMBER: P1011240

CATALOG NUMBER: S123DIP-B1165D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1536.1	1507.7	1451.8	1405.3	1358.8	1216.7	1031.6	826.8	627.0	461.4	349.7
115°	1491.0	1447.9	1374.5	1321.1	1267.7	1123.7	953.2	772.0	602.5	460.4	360.5
117.5°	1410.7	1362.7	1286.3	1230.9	1175.6	1043.3	892.5	735.7	585.8	461.4	374.2
120°	1327.4	1272.6	1195.2	1145.7	1096.2	978.7	846.4	708.3	575.1	465.3	389.9
122.5°	1238.3	1190.3	1123.7	1078.6	1033.5	926.8	810.2	685.8	568.2	472.2	404.6
125°	1163.8	1120.7	1058.0	1018.8	979.7	885.6	778.8	667.1	562.3	479.1	420.3
127.5°	1100.2	1062.9	1006.1	969.8	933.6	847.4	750.4	649.5	559.4	486.9	433.0
130°	1045.3	1010.0	958.1	924.8	891.5	812.1	724.0	635.8	556.4	494.7	445.7
132.5°	997.3	962.0	914.0	882.6	851.3	778.8	699.5	623.1	555.5	500.6	457.5
135°	944.4	915.0	867.0	839.1	811.2	747.5	677.9	612.3	554.5	506.5	467.3
137.5°	894.4	864.1	822.9	797.9	772.9	716.1	657.3	602.5	552.5	510.4	475.1
140°	843.5	816.1	778.8	757.8	736.7	689.7	639.7	593.7	551.5	514.3	481.0
142.5°	792.5	769.0	738.7	721.0	703.4	664.2	623.1	585.8	549.6	517.3	486.9
145°	747.5	726.9	702.4	688.2	674.0	642.7	610.3	579.0	547.6	518.2	490.8
147.5°	707.3	692.6	673.0	662.8	652.5	626.0	599.5	572.1	544.7	518.2	493.7
150°	675.0	664.2	649.5	640.2	630.9	610.3	587.8	565.3	540.8	518.2	494.7
152.5°	648.5	638.7	628.0	620.6	613.3	595.6	577.0	557.4	535.9	515.3	496.7
155°	625.0	617.2	608.4	602.5	596.6	581.9	566.2	549.6	530.0	513.3	496.7
157.5°	603.5	597.6	589.8	584.9	580.0	568.2	554.5	540.8	525.1	510.4	497.7
160°	584.9	579.0	572.1	568.7	565.3	555.5	544.7	532.0	519.2	508.4	497.7
162.5°	565.3	560.4	556.4	553.5	550.6	541.7	532.9	523.1	513.3	504.5	496.7
165°	548.6	544.7	540.8	538.3	535.9	529.0	523.1	515.3	507.5	500.6	494.7
167.5°	532.0	529.0	527.1	525.1	523.1	519.2	514.3	507.5	501.6	496.7	493.7
170°	517.3	515.3	514.3	513.3	512.4	508.4	505.5	500.6	495.7	492.8	490.8
172.5°	505.5	503.5	503.5	503.0	502.6	499.6	497.7	493.7	490.8	489.8	489.8
175°	494.7	493.7	493.7	493.7	493.7	491.8	490.8	488.8	486.9	486.9	487.9
177.5°	487.9	486.9	487.9	487.9	487.9	486.9	485.9	484.9	483.9	484.9	486.9
180°	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9

TEST NUMBER: P1011240

CATALOG NUMBER: S123DIP-B1165D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9
2.5°	1655.6	1651.0	1651.0	1647.8	1638.5	1621.3	1619.7	1622.8	1613.5	1604.1	1590.0
5°	1736.9	1707.2	1697.8	1688.4	1669.7	1638.5	1626.0	1615.0	1597.9	1577.5	1555.7
7.5°	1805.6	1763.4	1750.9	1733.7	1696.3	1652.5	1624.4	1601.0	1577.5	1549.4	1522.9
10°	1891.5	1830.6	1800.9	1775.9	1724.4	1663.5	1621.3	1586.9	1549.4	1515.1	1480.7
12.5°	1988.3	1889.9	1880.6	1819.6	1760.3	1669.7	1618.2	1568.2	1518.2	1476.0	1440.1
15°	2069.6	1961.8	1922.7	1882.1	1768.1	1655.6	1605.7	1549.4	1491.6	1446.3	1393.2
17.5°	2121.1	2032.1	1949.3	1894.6	1775.9	1675.9	1579.1	1515.1	1454.2	1391.7	1347.9
20°	2183.6	2053.9	1982.1	1908.7	1791.5	1660.3	1563.5	1483.8	1408.9	1352.6	1299.5
22.5°	2246.1	2071.1	2011.8	1932.1	1794.7	1644.7	1535.4	1455.7	1369.8	1313.6	1255.8
25°	2239.8	2096.1	1997.7	1930.5	1763.4	1630.7	1502.6	1408.9	1329.2	1257.4	1199.6
27.5°	2244.5	2068.0	1968.0	1889.9	1741.5	1610.3	1468.2	1369.8	1287.0	1212.1	1151.1
30°	2246.1	2025.8	1938.4	1844.6	1700.9	1561.9	1429.2	1329.2	1241.7	1160.5	1105.8
32.5°	2241.4	1991.5	1882.1	1797.8	1636.9	1515.1	1383.9	1277.7	1188.6	1113.7	1062.1
35°	2230.4	1950.8	1824.3	1718.1	1571.3	1447.9	1341.7	1232.4	1137.1	1068.4	1009.0
37.5°	2200.8	1907.1	1763.4	1658.8	1494.8	1369.8	1276.1	1185.5	1093.3	1012.1	962.1
40°	2178.9	1847.8	1702.5	1588.5	1412.0	1290.2	1212.1	1126.1	1035.6	962.1	913.7
42.5°	2128.9	1791.5	1640.0	1504.1	1330.8	1205.8	1132.4	1063.7	985.6	913.7	870.0
45°	2047.7	1730.6	1563.5	1426.0	1241.7	1123.0	1055.9	999.6	930.9	862.2	818.4
47.5°	1933.7	1643.1	1482.3	1344.8	1154.3	1034.0	966.8	924.7	870.0	812.2	774.7
50°	1810.3	1547.9	1399.5	1263.6	1069.9	952.8	887.2	848.1	812.2	759.1	723.2
52.5°	1649.4	1446.3	1304.2	1174.6	979.3	866.9	809.1	781.0	743.5	706.0	674.8
55°	1493.2	1315.1	1198.0	1074.6	890.3	785.6	729.4	699.7	677.9	646.6	621.6
57.5°	1312.0	1193.3	1085.5	973.1	807.5	712.2	659.1	623.2	609.2	595.1	571.7
60°	1144.9	1054.3	966.8	873.1	721.6	635.7	584.2	556.0	542.0	532.6	517.0
62.5°	991.8	921.5	846.6	771.6	634.1	556.0	517.0	488.9	476.4	474.8	460.8
65°	845.0	795.0	734.1	660.7	552.9	484.2	446.7	429.5	415.5	415.5	404.5
67.5°	698.2	663.8	615.4	563.9	479.5	415.5	381.1	365.5	357.7	357.7	349.9
70°	581.0	557.6	513.9	468.6	395.2	346.7	320.2	306.1	301.5	303.0	296.8
72.5°	471.7	446.7	410.8	378.0	323.3	287.4	268.7	253.0	245.2	246.8	245.2
75°	365.5	353.0	321.8	296.8	253.0	228.0	210.9	203.1	196.8	198.4	195.2
77.5°	274.9	256.2	239.0	221.8	195.2	174.9	160.9	153.1	148.4	148.4	148.4
80°	187.4	184.3	170.3	160.9	139.0	123.4	112.5	110.9	106.2	106.2	106.2
82.5°	121.8	114.0	106.2	100.0	87.5	78.1	73.4	70.3	68.7	67.2	70.3
85°	67.2	62.5	59.4	53.1	48.4	43.7	39.0	37.5	35.9	37.5	35.9
87.5°	26.6	21.9	21.9	20.3	18.7	17.2	17.2	14.1	14.1	12.5	12.5
90°	15.7	12.7	11.8	10.8	8.8	5.9	3.9	2.0	3.9	5.9	8.8
92.5°	98.9	67.6	58.8	50.0	40.2	31.3	21.6	14.7	21.6	31.3	40.2
95°	210.6	127.4	108.2	89.1	63.7	47.0	36.2	33.3	36.2	47.0	63.7
97.5°	227.3	145.0	124.0	102.9	77.4	62.7	53.9	52.9	53.9	62.7	77.4
100°	224.3	155.8	136.7	117.6	94.0	80.3	73.5	72.5	73.5	80.3	94.0
102.5°	228.3	168.5	151.4	134.2	113.6	100.9	95.0	93.1	95.0	100.9	113.6
105°	236.1	183.2	168.0	152.8	134.2	122.5	116.6	113.6	116.6	122.5	134.2
107.5°	248.8	201.8	187.6	173.4	155.8	144.0	138.1	135.2	138.1	144.0	155.8
110°	265.5	221.4	207.7	194.0	177.3	166.5	161.6	158.7	161.6	166.5	177.3

TEST NUMBER: P1011240

CATALOG NUMBER: S123DIP-B1165D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	282.1	242.0	228.8	215.5	198.9	188.1	183.2	180.3	183.2	188.1	198.9
115°	300.8	263.5	250.3	237.1	220.4	210.6	204.7	200.8	204.7	210.6	220.4
117.5°	320.3	283.1	270.8	258.6	240.0	231.2	226.3	221.4	226.3	231.2	240.0
120°	339.0	303.7	291.4	279.2	260.6	250.8	245.9	243.0	245.9	250.8	260.6
122.5°	358.6	324.3	311.0	297.8	280.2	269.4	264.5	261.6	264.5	269.4	280.2
125°	377.2	342.9	329.6	316.4	297.8	287.0	281.2	279.2	281.2	287.0	297.8
127.5°	393.8	360.5	347.3	334.1	313.5	302.7	295.9	292.9	295.9	302.7	313.5
130°	408.5	376.2	363.0	349.7	329.2	317.4	308.6	305.7	308.6	317.4	329.2
132.5°	421.3	389.9	377.2	364.4	343.9	329.2	319.4	315.4	319.4	329.2	343.9
135°	434.0	403.6	390.4	377.2	356.6	341.9	331.1	327.2	331.1	341.9	356.6
137.5°	442.8	413.4	401.2	388.9	368.4	352.7	341.9	338.0	341.9	352.7	368.4
140°	451.6	423.2	411.0	398.7	379.1	363.5	353.7	348.8	353.7	363.5	379.1
142.5°	458.5	431.0	419.8	408.5	388.9	375.2	364.4	360.5	364.4	375.2	388.9
145°	464.4	438.9	427.6	416.4	399.7	385.0	376.2	373.2	376.2	385.0	399.7
147.5°	469.3	445.7	436.0	426.2	409.5	396.8	387.9	386.0	387.9	396.8	409.5
150°	474.2	451.6	442.8	434.0	420.3	407.5	399.7	398.7	399.7	407.5	420.3
152.5°	477.1	458.5	450.2	441.8	430.1	419.3	411.5	411.5	411.5	419.3	430.1
155°	481.0	464.4	457.5	450.6	439.9	430.1	424.2	424.2	424.2	430.1	439.9
157.5°	483.0	469.3	463.9	458.5	448.7	439.9	435.0	434.0	435.0	439.9	448.7
160°	485.9	474.2	469.3	464.4	457.5	449.7	445.7	445.7	445.7	449.7	457.5
162.5°	486.9	477.1	473.2	469.3	463.4	457.5	454.6	454.6	454.6	457.5	463.4
165°	487.9	480.0	476.6	473.2	469.3	464.4	462.4	463.4	462.4	464.4	469.3
167.5°	487.9	482.0	479.6	477.1	474.2	470.2	469.3	470.2	469.3	470.2	474.2
170°	486.9	482.0	481.0	480.0	478.1	475.1	474.2	476.1	474.2	475.1	478.1
172.5°	486.9	483.0	482.5	482.0	481.0	479.1	479.1	480.0	479.1	479.1	481.0
175°	485.9	483.9	483.4	483.0	483.0	481.0	482.0	483.0	482.0	481.0	483.0
177.5°	484.9	483.9	483.9	483.9	483.9	483.0	483.9	484.9	483.9	483.0	483.9
180°	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9

TEST NUMBER: P1011240

CATALOG NUMBER: S123DIP-B1165D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9
2.5°	1586.9	1585.4	1588.5	1579.1	1563.5	1555.7	1533.8	1529.1	1527.6	1529.1	1530.7
5°	1543.2	1541.6	1536.9	1521.3	1502.6	1488.5	1462.0	1460.4	1451.0	1441.7	1446.3
7.5°	1501.0	1494.8	1485.4	1465.1	1440.1	1424.5	1402.6	1387.0	1374.5	1366.7	1360.4
10°	1458.8	1449.5	1440.1	1413.5	1382.3	1358.9	1332.3	1319.8	1305.8	1299.5	1293.3
12.5°	1404.2	1394.8	1377.6	1346.4	1327.6	1298.0	1271.4	1258.9	1251.1	1238.6	1230.8
15°	1360.4	1341.7	1332.3	1299.5	1260.5	1257.4	1208.9	1205.8	1190.2	1190.2	1177.7
17.5°	1310.5	1296.4	1279.2	1246.4	1218.3	1190.2	1165.2	1155.8	1141.8	1138.6	1132.4
20°	1262.0	1243.3	1237.0	1204.2	1174.6	1140.2	1113.7	1104.3	1098.0	1091.8	1096.5
22.5°	1212.1	1196.4	1180.8	1151.1	1129.3	1094.9	1079.3	1069.9	1060.5	1057.4	1059.0
25°	1163.6	1149.6	1134.0	1104.3	1080.9	1052.7	1038.7	1034.0	1029.3	1029.3	1027.7
27.5°	1116.8	1102.7	1088.7	1062.1	1038.7	1018.4	1007.4	1002.8	998.1	1001.2	1004.3
30°	1068.4	1055.9	1043.4	1019.9	1001.2	982.5	976.2	973.1	971.5	979.3	979.3
32.5°	1024.6	1013.7	1004.3	982.5	963.7	948.1	943.4	945.0	946.5	951.2	954.3
35°	979.3	971.5	962.1	943.4	927.8	913.7	915.3	915.3	918.4	926.2	932.5
37.5°	938.7	927.8	920.0	904.4	891.9	879.4	884.1	888.7	891.9	901.2	904.4
40°	890.3	885.6	879.4	863.7	852.8	851.3	852.8	855.9	862.2	866.9	871.6
42.5°	851.3	845.0	837.2	824.7	815.3	816.9	818.4	821.6	824.7	832.5	837.2
45°	807.5	802.8	796.6	785.6	777.8	779.4	781.0	781.0	784.1	793.5	796.6
47.5°	759.1	760.7	752.8	741.9	737.2	737.2	737.2	740.4	748.2	751.3	752.8
50°	712.2	709.1	707.6	696.6	693.5	691.9	693.5	695.1	706.0	704.4	709.1
52.5°	662.3	662.3	660.7	654.4	649.8	649.8	646.6	654.4	657.6	660.7	665.4
55°	613.8	609.2	607.6	604.5	598.2	596.7	599.8	609.2	612.3	615.4	620.1
57.5°	560.7	560.7	557.6	552.9	552.9	552.9	552.9	559.2	563.9	567.0	576.4
60°	512.3	506.1	501.4	501.4	501.4	499.8	509.2	509.2	518.6	520.1	523.2
62.5°	454.5	451.4	448.3	449.8	448.3	451.4	454.5	460.8	462.3	467.0	471.7
65°	399.9	399.9	396.7	406.1	399.9	399.9	407.7	407.7	410.8	415.5	421.7
67.5°	346.7	348.3	345.2	345.2	348.3	349.9	351.4	357.7	359.2	365.5	373.3
70°	292.1	295.2	296.8	293.6	296.8	299.9	303.0	304.6	310.8	313.9	318.6
72.5°	243.7	246.8	242.1	243.7	245.2	248.3	249.9	253.0	256.2	265.5	268.7
75°	195.2	193.7	192.1	198.4	195.2	201.5	203.1	203.1	206.2	214.0	217.1
77.5°	149.9	149.9	151.5	148.4	153.1	151.5	153.1	157.8	162.4	162.4	174.9
80°	104.6	107.8	107.8	107.8	109.3	110.9	107.8	115.6	117.1	117.1	121.8
82.5°	67.2	68.7	67.2	70.3	70.3	73.4	71.8	73.4	76.5	79.7	81.2
85°	35.9	35.9	39.0	39.0	37.5	39.0	37.5	39.0	42.2	42.2	43.7
87.5°	12.5	12.5	12.5	12.5	14.1	12.5	14.1	14.1	12.5	12.5	17.2
90°	10.8	11.8	12.7	15.7	18.6	21.6	24.5	23.5	24.5	25.5	26.5
92.5°	50.0	58.8	67.6	98.9	150.9	201.8	182.2	136.2	97.0	75.4	65.6
95°	89.1	108.2	127.4	210.6	356.6	517.3	580.9	471.2	352.7	239.0	187.1
97.5°	102.9	124.0	145.0	227.3	396.8	667.1	893.4	923.8	810.2	611.3	482.0
100°	117.6	136.7	155.8	224.3	369.3	627.0	927.7	1120.7	1155.0	1075.7	961.0
102.5°	134.2	151.4	168.5	228.3	345.8	568.2	864.1	1130.5	1269.6	1286.3	1231.4
105°	152.8	168.0	183.2	236.1	337.0	522.2	787.6	1068.8	1273.6	1371.5	1390.1
107.5°	173.4	187.6	201.8	248.8	335.0	488.8	720.0	980.6	1214.8	1368.6	1445.0
110°	194.0	207.7	221.4	265.5	339.9	471.2	664.2	898.3	1122.7	1302.9	1426.4

TEST NUMBER: P1011240

CATALOG NUMBER: S123DIP-B1165D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	215.5	228.8	242.0	282.1	349.7	461.4	627.0	826.8	1031.6	1216.7	1358.8
115°	237.1	250.3	263.5	300.8	360.5	460.4	602.5	772.0	953.2	1123.7	1267.7
117.5°	258.6	270.8	283.1	320.3	374.2	461.4	585.8	735.7	892.5	1043.3	1175.6
120°	279.2	291.4	303.7	339.0	389.9	465.3	575.1	708.3	846.4	978.7	1096.2
122.5°	297.8	311.0	324.3	358.6	404.6	472.2	568.2	685.8	810.2	926.8	1033.5
125°	316.4	329.6	342.9	377.2	420.3	479.1	562.3	667.1	778.8	885.6	979.7
127.5°	334.1	347.3	360.5	393.8	433.0	486.9	559.4	649.5	750.4	847.4	933.6
130°	349.7	363.0	376.2	408.5	445.7	494.7	556.4	635.8	724.0	812.1	891.5
132.5°	364.4	377.2	389.9	421.3	457.5	500.6	555.5	623.1	699.5	778.8	851.3
135°	377.2	390.4	403.6	434.0	467.3	506.5	554.5	612.3	677.9	747.5	811.2
137.5°	388.9	401.2	413.4	442.8	475.1	510.4	552.5	602.5	657.3	716.1	772.9
140°	398.7	411.0	423.2	451.6	481.0	514.3	551.5	593.7	639.7	689.7	736.7
142.5°	408.5	419.8	431.0	458.5	486.9	517.3	549.6	585.8	623.1	664.2	703.4
145°	416.4	427.6	438.9	464.4	490.8	518.2	547.6	579.0	610.3	642.7	674.0
147.5°	426.2	436.0	445.7	469.3	493.7	518.2	544.7	572.1	599.5	626.0	652.5
150°	434.0	442.8	451.6	474.2	494.7	518.2	540.8	565.3	587.8	610.3	630.9
152.5°	441.8	450.2	458.5	477.1	496.7	515.3	535.9	557.4	577.0	595.6	613.3
155°	450.6	457.5	464.4	481.0	496.7	513.3	530.0	549.6	566.2	581.9	596.6
157.5°	458.5	463.9	469.3	483.0	497.7	510.4	525.1	540.8	554.5	568.2	580.0
160°	464.4	469.3	474.2	485.9	497.7	508.4	519.2	532.0	544.7	555.5	565.3
162.5°	469.3	473.2	477.1	486.9	496.7	504.5	513.3	523.1	532.9	541.7	550.6
165°	473.2	476.6	480.0	487.9	494.7	500.6	507.5	515.3	523.1	529.0	535.9
167.5°	477.1	479.6	482.0	487.9	493.7	496.7	501.6	507.5	514.3	519.2	523.1
170°	480.0	481.0	482.0	486.9	490.8	492.8	495.7	500.6	505.5	508.4	512.4
172.5°	482.0	482.5	483.0	486.9	489.8	489.8	490.8	493.7	497.7	499.6	502.6
175°	483.0	483.4	483.9	485.9	487.9	486.9	486.9	488.8	490.8	491.8	493.7
177.5°	483.9	483.9	483.9	484.9	486.9	484.9	483.9	484.9	485.9	486.9	487.9
180°	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9

TEST NUMBER: P1011240

CATALOG NUMBER: S123DIP-B1165D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9
2.5°	1529.1	1530.7	1524.4	1519.8	1532.3	1524.4	1524.4	1526.0	1522.9	1527.6	1526.0
5°	1443.2	1444.8	1433.8	1437.0	1430.7	1429.2	1427.6	1437.0	1435.4	1433.8	1437.0
7.5°	1358.9	1358.9	1354.2	1351.1	1351.1	1346.4	1352.6	1351.1	1354.2	1354.2	1358.9
10°	1288.6	1291.7	1283.9	1276.1	1274.5	1276.1	1276.1	1277.7	1279.2	1290.2	1288.6
12.5°	1230.8	1226.1	1224.6	1219.9	1212.1	1208.9	1205.8	1223.0	1218.3	1218.3	1218.3
15°	1166.8	1177.7	1176.1	1162.1	1159.0	1165.2	1162.1	1162.1	1177.7	1176.1	1174.6
17.5°	1132.4	1129.3	1126.1	1118.3	1119.9	1118.3	1119.9	1119.9	1129.3	1129.3	1129.3
20°	1093.3	1087.1	1087.1	1084.0	1084.0	1079.3	1085.5	1087.1	1093.3	1093.3	1094.9
22.5°	1059.0	1054.3	1054.3	1052.7	1055.9	1049.6	1055.9	1057.4	1057.4	1062.1	1062.1
25°	1029.3	1026.2	1026.2	1029.3	1029.3	1029.3	1029.3	1035.6	1030.9	1032.4	1030.9
27.5°	1002.8	1004.3	1005.9	1007.4	1005.9	1007.4	1009.0	1012.1	1013.7	1012.1	1009.0
30°	977.8	982.5	984.0	984.0	987.1	988.7	990.3	990.3	991.8	987.1	990.3
32.5°	959.0	959.0	962.1	963.7	966.8	968.4	968.4	971.5	970.0	965.3	966.8
35°	932.5	932.5	938.7	941.8	946.5	945.0	946.5	946.5	948.1	945.0	940.3
37.5°	905.9	909.0	909.0	915.3	916.9	918.4	916.9	920.0	918.4	915.3	913.7
40°	874.7	873.1	874.7	879.4	880.9	880.9	880.9	884.1	884.1	884.1	882.5
42.5°	835.6	840.3	838.8	843.4	841.9	841.9	845.0	848.1	849.7	845.0	846.6
45°	798.1	798.1	801.3	801.3	802.8	802.8	809.1	806.0	809.1	806.0	807.5
47.5°	757.5	759.1	759.1	760.7	763.8	766.9	763.8	765.3	765.3	766.9	763.8
50°	712.2	712.2	715.4	720.0	726.3	723.2	721.6	727.9	723.2	723.2	720.0
52.5°	665.4	670.1	671.6	676.3	681.0	682.6	684.1	681.0	682.6	677.9	679.4
55°	620.1	621.6	627.9	632.6	637.3	637.3	635.7	637.3	638.8	632.6	632.6
57.5°	574.8	579.5	585.7	585.7	592.0	592.0	590.4	590.4	592.0	587.3	585.7
60°	526.4	531.1	538.9	538.9	548.2	549.8	546.7	543.6	543.6	538.9	540.4
62.5°	474.8	479.5	484.2	492.0	498.3	495.1	501.4	495.1	496.7	487.3	487.3
65°	429.5	431.1	438.9	446.7	446.7	449.8	446.7	448.3	443.6	443.6	437.3
67.5°	376.4	376.4	384.2	392.0	399.9	399.9	399.9	395.2	395.2	390.5	390.5
70°	329.6	328.0	335.8	340.5	345.2	346.7	343.6	342.1	338.9	334.3	332.7
72.5°	271.8	274.9	282.7	285.8	293.6	292.1	299.9	290.5	290.5	282.7	281.1
75°	220.2	223.4	231.2	235.9	240.5	240.5	245.2	240.5	234.3	231.2	229.6
77.5°	174.9	173.4	179.6	187.4	189.0	187.4	190.6	189.0	182.7	182.7	179.6
80°	125.0	129.6	135.9	134.3	140.6	139.0	139.0	135.9	135.9	131.2	134.3
82.5°	82.8	87.5	89.0	87.5	89.0	92.2	93.7	92.2	92.2	89.0	90.6
85°	43.7	43.7	46.9	48.4	46.9	46.9	48.4	53.1	50.0	46.9	50.0
87.5°	14.1	12.5	12.5	14.1	12.5	12.5	14.1	14.1	15.6	15.6	15.6
90°	27.4	28.4	27.4	28.4	29.4	28.4	29.4	28.4	27.4	28.4	27.4
92.5°	62.2	58.8	56.8	52.9	53.9	51.9	53.9	52.9	56.8	58.8	62.2
95°	169.4	151.8	133.2	124.4	117.6	113.6	117.6	124.4	133.2	151.8	169.4
97.5°	426.2	370.3	304.7	267.4	243.9	233.2	243.9	267.4	304.7	370.3	426.2
100°	891.4	821.9	723.0	651.5	613.3	614.2	613.3	651.5	723.0	821.9	891.4
102.5°	1193.7	1156.0	1084.5	1031.6	1001.2	972.8	1001.2	1031.6	1084.5	1156.0	1193.7
105°	1377.4	1364.7	1319.6	1282.4	1251.0	1246.1	1251.0	1282.4	1319.6	1364.7	1377.4
107.5°	1458.2	1471.4	1465.6	1447.9	1435.2	1424.4	1435.2	1447.9	1465.6	1471.4	1458.2
110°	1460.7	1495.0	1522.4	1530.2	1528.3	1526.3	1528.3	1530.2	1522.4	1495.0	1460.7

TEST NUMBER: P1011240

CATALOG NUMBER: S123DIP-B1165D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1405.3	1451.8	1507.7	1536.1	1545.9	1546.9	1545.9	1536.1	1507.7	1451.8	1405.3
115°	1321.1	1374.5	1447.9	1491.0	1510.6	1515.5	1510.6	1491.0	1447.9	1374.5	1321.1
117.5°	1230.9	1286.3	1362.7	1410.7	1440.1	1447.0	1440.1	1410.7	1362.7	1286.3	1230.9
120°	1145.7	1195.2	1272.6	1327.4	1350.9	1356.8	1350.9	1327.4	1272.6	1195.2	1145.7
122.5°	1078.6	1123.7	1190.3	1238.3	1264.7	1272.6	1264.7	1238.3	1190.3	1123.7	1078.6
125°	1018.8	1058.0	1120.7	1163.8	1188.3	1195.2	1188.3	1163.8	1120.7	1058.0	1018.8
127.5°	969.8	1006.1	1062.9	1100.2	1122.7	1128.6	1122.7	1100.2	1062.9	1006.1	969.8
130°	924.8	958.1	1010.0	1045.3	1065.9	1073.7	1065.9	1045.3	1010.0	958.1	924.8
132.5°	882.6	914.0	962.0	997.3	1014.9	1019.8	1014.9	997.3	962.0	914.0	882.6
135°	839.1	867.0	915.0	944.4	962.0	968.9	962.0	944.4	915.0	867.0	839.1
137.5°	797.9	822.9	864.1	894.4	909.1	915.0	909.1	894.4	864.1	822.9	797.9
140°	757.8	778.8	816.1	843.5	859.2	858.2	859.2	843.5	816.1	778.8	757.8
142.5°	721.0	738.7	769.0	792.5	806.3	805.3	806.3	792.5	769.0	738.7	721.0
145°	688.2	702.4	726.9	747.5	755.3	757.3	755.3	747.5	726.9	702.4	688.2
147.5°	662.8	673.0	692.6	707.3	715.1	716.1	715.1	707.3	692.6	673.0	662.8
150°	640.2	649.5	664.2	675.0	680.9	680.9	680.9	675.0	664.2	649.5	640.2
152.5°	620.6	628.0	638.7	648.5	651.5	651.5	651.5	648.5	638.7	628.0	620.6
155°	602.5	608.4	617.2	625.0	627.0	628.0	627.0	625.0	617.2	608.4	602.5
157.5°	584.9	589.8	597.6	603.5	605.4	605.4	605.4	603.5	597.6	589.8	584.9
160°	568.7	572.1	579.0	584.9	584.9	583.9	584.9	584.9	579.0	572.1	568.7
162.5°	553.5	556.4	560.4	565.3	565.3	564.3	565.3	565.3	560.4	556.4	553.5
165°	538.3	540.8	544.7	548.6	547.6	547.6	547.6	548.6	544.7	540.8	538.3
167.5°	525.1	527.1	529.0	532.0	531.0	531.0	531.0	532.0	529.0	527.1	525.1
170°	513.3	514.3	515.3	517.3	516.3	516.3	516.3	517.3	515.3	514.3	513.3
172.5°	503.0	503.5	503.5	505.5	503.5	502.6	503.5	505.5	503.5	503.5	503.0
175°	493.7	493.7	493.7	494.7	493.7	492.8	493.7	494.7	493.7	493.7	493.7
177.5°	487.9	487.9	486.9	487.9	485.9	485.9	485.9	487.9	486.9	487.9	487.9
180°	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9

TEST NUMBER: P1011240

CATALOG NUMBER: S123DIP-B1165D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9
2.5°	1530.7	1533.8	1535.4	1529.1	1524.4	1532.3	1543.2	1551.0	1557.2	1565.1	1569.7
5°	1440.1	1451.0	1451.0	1454.2	1458.8	1466.6	1487.0	1501.0	1513.5	1522.9	1530.7
7.5°	1363.6	1371.4	1376.1	1383.9	1391.7	1402.6	1426.0	1446.3	1465.1	1476.0	1488.5
10°	1294.8	1301.1	1308.9	1313.6	1327.6	1343.3	1372.9	1390.1	1412.0	1429.2	1444.8
12.5°	1229.2	1251.1	1255.8	1254.2	1266.7	1283.9	1313.6	1340.1	1363.6	1380.7	1397.9
15°	1182.4	1190.2	1199.6	1198.0	1224.6	1229.2	1254.2	1285.5	1316.7	1327.6	1343.3
17.5°	1130.8	1143.3	1152.7	1157.4	1165.2	1182.4	1205.8	1229.2	1269.8	1271.4	1312.0
20°	1090.2	1102.7	1109.0	1115.2	1119.9	1140.2	1160.5	1187.1	1219.9	1237.0	1258.9
22.5°	1063.7	1069.9	1074.6	1079.3	1085.5	1096.5	1121.5	1151.1	1173.0	1191.8	1205.8
25°	1032.4	1038.7	1044.9	1048.1	1052.7	1059.0	1077.7	1101.2	1132.4	1144.9	1159.0
27.5°	1010.6	1010.6	1013.7	1013.7	1019.9	1026.2	1040.2	1062.1	1087.1	1102.7	1121.5
30°	987.1	985.6	987.1	985.6	984.0	993.4	1005.9	1024.6	1041.8	1060.5	1073.0
32.5°	963.7	962.1	962.1	963.7	957.5	962.1	968.4	985.6	1004.3	1013.7	1027.7
35°	938.7	935.6	935.6	935.6	932.5	929.3	935.6	951.2	963.7	976.2	987.1
37.5°	913.7	909.0	909.0	905.9	902.8	898.1	898.1	910.6	927.8	932.5	946.5
40°	879.4	879.4	876.2	874.7	871.6	868.4	863.7	874.7	890.3	895.0	905.9
42.5°	845.0	840.3	838.8	838.8	838.8	834.1	830.9	838.8	848.1	855.9	862.2
45°	806.0	802.8	804.4	802.8	799.7	798.1	796.6	799.7	810.6	813.8	821.6
47.5°	763.8	762.2	762.2	760.7	759.1	760.7	754.4	762.2	765.3	768.5	774.7
50°	720.0	718.5	716.9	715.4	715.4	716.9	715.4	715.4	721.6	724.7	731.0
52.5°	676.3	671.6	671.6	670.1	670.1	666.9	670.1	671.6	674.8	677.9	681.0
55°	629.5	629.5	624.8	624.8	621.6	621.6	623.2	621.6	627.9	631.0	631.0
57.5°	584.2	577.9	579.5	576.4	573.2	571.7	571.7	574.8	577.9	577.9	581.0
60°	535.7	529.5	527.9	521.7	524.8	520.1	521.7	521.7	527.9	524.8	527.9
62.5°	487.3	479.5	474.8	471.7	471.7	473.3	470.1	468.6	471.7	474.8	481.1
65°	435.8	431.1	426.4	421.7	421.7	420.2	423.3	418.6	417.0	418.6	421.7
67.5°	382.7	378.0	373.3	368.6	370.2	365.5	362.4	367.1	363.9	365.5	368.6
70°	331.1	328.0	318.6	315.5	313.9	315.5	313.9	310.8	315.5	313.9	315.5
72.5°	279.6	276.5	271.8	264.0	264.0	262.4	260.8	260.8	259.3	259.3	259.3
75°	229.6	223.4	218.7	217.1	214.0	212.4	210.9	207.7	209.3	210.9	207.7
77.5°	178.1	170.3	168.7	168.7	164.0	164.0	165.6	164.0	162.4	162.4	162.4
80°	131.2	125.0	125.0	121.8	118.7	118.7	118.7	118.7	117.1	115.6	117.1
82.5°	84.3	82.8	81.2	81.2	84.3	78.1	81.2	79.7	78.1	78.1	76.5
85°	46.9	48.4	46.9	48.4	45.3	46.9	46.9	46.9	45.3	46.9	43.7
87.5°	17.2	17.2	17.2	18.7	18.7	18.7	18.7	18.7	20.3	18.7	18.7
90°	26.5	25.5	24.5	23.5	24.5	21.6	18.6	15.7	12.7	11.8	10.8
92.5°	65.6	75.4	97.0	136.2	182.2	201.8	150.9	98.9	67.6	58.8	50.0
95°	187.1	239.0	352.7	471.2	580.9	517.3	356.6	210.6	127.4	108.2	89.1
97.5°	482.0	611.3	810.2	923.8	893.4	667.1	396.8	227.3	145.0	124.0	102.9
100°	961.0	1075.7	1155.0	1120.7	927.7	627.0	369.3	224.3	155.8	136.7	117.6
102.5°	1231.4	1286.3	1269.6	1130.5	864.1	568.2	345.8	228.3	168.5	151.4	134.2
105°	1390.1	1371.5	1273.6	1068.8	787.6	522.2	337.0	236.1	183.2	168.0	152.8
107.5°	1445.0	1368.6	1214.8	980.6	720.0	488.8	335.0	248.8	201.8	187.6	173.4
110°	1426.4	1302.9	1122.7	898.3	664.2	471.2	339.9	265.5	221.4	207.7	194.0

TEST NUMBER: P1011240

CATALOG NUMBER: S123DIP-B1165D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1358.8	1216.7	1031.6	826.8	627.0	461.4	349.7	282.1	242.0	228.8	215.5
115°	1267.7	1123.7	953.2	772.0	602.5	460.4	360.5	300.8	263.5	250.3	237.1
117.5°	1175.6	1043.3	892.5	735.7	585.8	461.4	374.2	320.3	283.1	270.8	258.6
120°	1096.2	978.7	846.4	708.3	575.1	465.3	389.9	339.0	303.7	291.4	279.2
122.5°	1033.5	926.8	810.2	685.8	568.2	472.2	404.6	358.6	324.3	311.0	297.8
125°	979.7	885.6	778.8	667.1	562.3	479.1	420.3	377.2	342.9	329.6	316.4
127.5°	933.6	847.4	750.4	649.5	559.4	486.9	433.0	393.8	360.5	347.3	334.1
130°	891.5	812.1	724.0	635.8	556.4	494.7	445.7	408.5	376.2	363.0	349.7
132.5°	851.3	778.8	699.5	623.1	555.5	500.6	457.5	421.3	389.9	377.2	364.4
135°	811.2	747.5	677.9	612.3	554.5	506.5	467.3	434.0	403.6	390.4	377.2
137.5°	772.9	716.1	657.3	602.5	552.5	510.4	475.1	442.8	413.4	401.2	388.9
140°	736.7	689.7	639.7	593.7	551.5	514.3	481.0	451.6	423.2	411.0	398.7
142.5°	703.4	664.2	623.1	585.8	549.6	517.3	486.9	458.5	431.0	419.8	408.5
145°	674.0	642.7	610.3	579.0	547.6	518.2	490.8	464.4	438.9	427.6	416.4
147.5°	652.5	626.0	599.5	572.1	544.7	518.2	493.7	469.3	445.7	436.0	426.2
150°	630.9	610.3	587.8	565.3	540.8	518.2	494.7	474.2	451.6	442.8	434.0
152.5°	613.3	595.6	577.0	557.4	535.9	515.3	496.7	477.1	458.5	450.2	441.8
155°	596.6	581.9	566.2	549.6	530.0	513.3	496.7	481.0	464.4	457.5	450.6
157.5°	580.0	568.2	554.5	540.8	525.1	510.4	497.7	483.0	469.3	463.9	458.5
160°	565.3	555.5	544.7	532.0	519.2	508.4	497.7	485.9	474.2	469.3	464.4
162.5°	550.6	541.7	532.9	523.1	513.3	504.5	496.7	486.9	477.1	473.2	469.3
165°	535.9	529.0	523.1	515.3	507.5	500.6	494.7	487.9	480.0	476.6	473.2
167.5°	523.1	519.2	514.3	507.5	501.6	496.7	493.7	487.9	482.0	479.6	477.1
170°	512.4	508.4	505.5	500.6	495.7	492.8	490.8	486.9	482.0	481.0	480.0
172.5°	502.6	499.6	497.7	493.7	490.8	489.8	489.8	486.9	483.0	482.5	482.0
175°	493.7	491.8	490.8	488.8	486.9	486.9	487.9	485.9	483.9	483.4	483.0
177.5°	487.9	486.9	485.9	484.9	483.9	484.9	486.9	484.9	483.9	483.9	483.9
180°	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9

TEST NUMBER: P1011240

CATALOG NUMBER: S123DIP-B1165D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1611.9	1611.9	1611.9	1611.9
2.5°	1577.5	1582.2	1597.9	1616.6
5°	1546.3	1558.8	1580.7	1610.3
7.5°	1511.9	1530.7	1561.9	1599.4
10°	1472.9	1499.5	1538.5	1585.4
12.5°	1430.7	1465.1	1515.1	1563.5
15°	1404.2	1438.5	1483.8	1536.9
17.5°	1352.6	1393.2	1440.1	1515.1
20°	1299.5	1344.8	1405.7	1480.7
22.5°	1258.9	1307.3	1365.1	1444.8
25°	1210.5	1260.5	1323.0	1405.7
27.5°	1159.0	1208.9	1279.2	1366.7
30°	1119.9	1168.3	1235.5	1329.2
32.5°	1073.0	1119.9	1190.2	1288.6
35°	1019.9	1073.0	1140.2	1240.2
37.5°	979.3	1027.7	1098.0	1193.3
40°	935.6	977.8	1046.5	1140.2
42.5°	888.7	935.6	994.9	1088.7
45°	845.0	879.4	940.3	1029.3
47.5°	798.1	837.2	884.1	952.8
50°	748.2	781.0	832.5	879.4
52.5°	699.7	726.3	770.0	806.0
55°	648.2	674.8	707.6	729.4
57.5°	599.8	618.5	640.4	654.4
60°	540.4	559.2	573.2	587.3
62.5°	487.3	501.4	509.2	517.0
65°	432.7	440.5	445.1	451.4
67.5°	373.3	381.1	382.7	392.0
70°	318.6	320.2	323.3	328.0
72.5°	267.1	270.2	268.7	271.8
75°	214.0	217.1	214.0	217.1
77.5°	162.4	165.6	165.6	170.3
80°	117.1	118.7	120.3	120.3
82.5°	76.5	81.2	78.1	79.7
85°	43.7	45.3	45.3	46.9
87.5°	20.3	21.9	20.3	23.4
90°	8.8	5.9	3.9	2.0
92.5°	40.2	31.3	21.6	14.7
95°	63.7	47.0	36.2	33.3
97.5°	77.4	62.7	53.9	52.9
100°	94.0	80.3	73.5	72.5
102.5°	113.6	100.9	95.0	93.1
105°	134.2	122.5	116.6	113.6
107.5°	155.8	144.0	138.1	135.2
110°	177.3	166.5	161.6	158.7

TEST NUMBER: P1011240

CATALOG NUMBER: S123DIP-B1165D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	198.9	188.1	183.2	180.3
115°	220.4	210.6	204.7	200.8
117.5°	240.0	231.2	226.3	221.4
120°	260.6	250.8	245.9	243.0
122.5°	280.2	269.4	264.5	261.6
125°	297.8	287.0	281.2	279.2
127.5°	313.5	302.7	295.9	292.9
130°	329.2	317.4	308.6	305.7
132.5°	343.9	329.2	319.4	315.4
135°	356.6	341.9	331.1	327.2
137.5°	368.4	352.7	341.9	338.0
140°	379.1	363.5	353.7	348.8
142.5°	388.9	375.2	364.4	360.5
145°	399.7	385.0	376.2	373.2
147.5°	409.5	396.8	387.9	386.0
150°	420.3	407.5	399.7	398.7
152.5°	430.1	419.3	411.5	411.5
155°	439.9	430.1	424.2	424.2
157.5°	448.7	439.9	435.0	434.0
160°	457.5	449.7	445.7	445.7
162.5°	463.4	457.5	454.6	454.6
165°	469.3	464.4	462.4	463.4
167.5°	474.2	470.2	469.3	470.2
170°	478.1	475.1	474.2	476.1
172.5°	481.0	479.1	479.1	480.0
175°	483.0	481.0	482.0	483.0
177.5°	483.9	483.0	483.9	484.9
180°	483.9	483.9	483.9	483.9

(END OF REPORT)