

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011381

Luminaire Tested: S123DIP-B1165D585UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011381
REPORT IS A COMBINATION OF REPORTS P989525 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1165D585UB30-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7032.0 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011381

CATALOG NUMBER: S123DIP-B1165D585UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1011381

CATALOG NUMBER: S123DIP-B1165D585UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	74	74	74
1	103	98	94	91	97	93	90	87	83	81	79	75	73	71	66	65	64	64	64	60
2	94	86	80	75	88	82	76	72	74	69	66	66	63	60	59	56	54	54	54	51
3	86	76	69	63	81	72	66	60	65	60	56	59	54	51	52	49	46	46	46	43
4	79	68	60	54	74	64	57	52	58	52	48	52	48	44	47	43	40	40	40	37
5	72	61	52	46	68	58	50	45	52	46	41	47	42	38	43	39	35	35	35	33
6	67	55	46	40	63	52	44	39	47	41	36	43	38	34	39	34	31	31	31	29
7	62	49	41	36	58	47	40	34	43	37	32	39	34	30	35	31	28	28	28	25
8	58	45	37	32	54	43	36	31	39	33	29	36	31	27	32	28	25	25	25	23
9	54	41	34	28	51	39	32	28	36	30	26	33	28	24	30	26	23	23	23	21
10	50	38	30	26	48	36	29	25	33	27	23	30	25	22	28	24	21	21	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17500	17500	17500	17500
5°	17511	20164	17563	15049
10°	17400	24401	17418	13141
15°	17160	28938	17299	11829
20°	16953	33317	16989	10885
25°	16646	34156	16682	10392
30°	16427	28220	16427	10069
35°	16154	18873	16052	9784
40°	15828	13624	15633	9347
45°	15419	10792	14974	8805
50°	14424	9165	13910	8271
55°	13330	8053	12789	7677
60°	12224	7012	11572	7052
65°	11006	6005	10472	6220
70°	9742	4984	9094	5243
75°	8331	3759	7790	4047
80°	6585	2509	6075	2659
85°	4543	1153	3631	1048

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 28223 cd/sqm

TEST NUMBER: P1011381

CATALOG NUMBER: S123DIP-B1165D585UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.9	2.3
10°-20°	513.6	7.3
20°-30°	864.1	12.3
30°-40°	976.5	13.9
40°-50°	874.6	12.4
50°-60°	706.1	10.0
60°-70°	492.0	7.0
70°-80°	258.2	3.7
80°-90°	63.5	0.9
90°-100°	153.2	2.2
100°-110°	448.5	6.4
110°-120°	437.9	6.2
120°-130°	348.8	5.0
130°-140°	275.2	3.9
140°-150°	205.3	2.9
150°-160°	143.1	2.0
160°-170°	84.1	1.2
170°-180°	27.3	0.4
0°-30°	1537.6	21.9
0°-40°	2514.1	35.8
0°-60°	4094.8	58.2
0°-90°	4908.6	69.8
90°-120°	1039.6	14.8
90°-150°	1868.9	26.6
90°-180°	2123.0	30.2
0°-180°	7032.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1626	1626	1626	1626	1626	
5°	1624	1932	1629	1442	1624	154
15°	1550	2875	1563	1175	1550	438
25°	1418	3412	1421	1038	1418	654
35°	1251	1838	1243	953	1251	783
45°	1038	992	1008	810	1038	794
55°	736	674	706	643	736	659
65°	455	438	433	454	455	453
75°	219	225	205	243	219	235
85°	47	52	38	47	47	54
90°	1	17	1	17	1	5
95°	19	66	19	66	19	21
105°	66	727	66	727	66	70
115°	117	884	117	884	117	116
125°	163	697	163	697	163	145
135°	191	565	191	565	191	147
145°	218	442	218	442	218	136
155°	247	366	247	366	247	114
165°	270	319	270	319	270	76
175°	282	287	282	287	282	27
180°	282	282	282	282	282	

TEST NUMBER: P1011381

CATALOG NUMBER: S123DIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8
2.5°	1630.6	1643.2	1649.5	1658.9	1668.4	1682.5	1687.3	1695.1	1692.0	1698.3	1701.4
5°	1624.2	1646.3	1665.2	1688.8	1710.9	1726.7	1742.4	1767.6	1786.5	1789.7	1803.8
7.5°	1613.2	1644.7	1677.8	1710.9	1753.4	1778.6	1807.0	1841.7	1870.0	1915.7	1933.0
10°	1599.0	1643.2	1690.4	1736.1	1794.4	1833.8	1868.4	1926.7	1985.0	2032.3	2076.4
12.5°	1577.0	1632.1	1693.6	1761.3	1836.9	1882.6	1929.9	2007.1	2095.3	2167.8	2215.0
15°	1550.2	1619.5	1698.3	1770.8	1854.3	1939.3	1989.7	2076.4	2202.4	2270.2	2391.5
17.5°	1528.1	1599.0	1677.8	1791.2	1904.7	1989.7	2026.0	2185.1	2271.7	2385.2	2522.2
20°	1493.5	1583.3	1684.1	1797.5	1944.1	1996.0	2070.1	2230.8	2337.9	2486.0	2654.6
22.5°	1457.3	1553.4	1674.7	1792.8	1956.7	2011.8	2112.6	2240.2	2410.4	2556.9	2742.8
25°	1417.9	1521.8	1644.7	1784.9	1945.6	2026.0	2120.5	2278.0	2462.4	2646.7	2818.4
27.5°	1378.5	1491.9	1619.5	1759.7	1915.7	2010.2	2104.7	2268.6	2504.9	2705.0	2924.0
30°	1340.7	1454.1	1581.7	1725.1	1888.9	1980.3	2070.1	2274.9	2538.0	2763.3	2983.8
32.5°	1299.7	1416.3	1550.2	1669.9	1835.4	1933.0	2033.9	2274.9	2558.5	2797.9	2999.6
35°	1250.9	1370.6	1485.6	1605.3	1769.2	1877.9	1991.3	2259.1	2577.4	2809.0	2933.4
37.5°	1203.6	1309.2	1408.4	1525.0	1696.7	1813.3	1944.1	2240.2	2567.9	2761.7	2796.4
40°	1150.1	1255.6	1335.9	1444.7	1625.8	1761.3	1893.6	2215.0	2527.0	2649.8	2549.0
42.5°	1098.1	1181.6	1250.9	1356.4	1553.4	1685.7	1829.1	2169.3	2446.6	2471.8	2245.0
45°	1038.2	1098.1	1159.5	1279.2	1474.6	1610.1	1769.2	2103.2	2317.4	2245.0	1958.2
47.5°	961.0	1014.6	1082.3	1192.6	1391.1	1531.3	1682.5	2018.1	2130.0	1978.7	1665.2
50°	887.0	932.6	995.7	1102.8	1302.9	1439.9	1600.6	1884.2	1939.3	1701.4	1435.2
52.5°	812.9	847.6	909.0	1016.1	1216.2	1348.6	1495.1	1747.1	1715.6	1460.4	1224.1
55°	735.7	765.6	823.9	929.5	1115.4	1241.4	1381.6	1578.6	1496.6	1254.0	1065.0
57.5°	660.1	691.6	751.5	839.7	1014.6	1137.4	1249.3	1403.7	1280.8	1087.0	920.0
60°	592.4	619.1	664.8	751.5	910.6	1009.8	1112.2	1217.8	1115.4	927.9	800.3
62.5°	521.5	546.7	589.2	668.0	805.0	893.3	975.2	1061.8	948.4	811.3	697.9
65°	455.3	475.8	515.2	587.6	699.5	772.0	838.1	898.0	806.6	680.6	595.5
67.5°	395.4	412.8	445.8	510.4	605.0	656.9	710.5	760.9	683.7	582.9	510.4
70°	330.8	345.0	374.9	422.2	497.8	551.4	590.8	628.6	559.3	478.9	430.1
72.5°	274.1	288.3	307.2	356.0	408.0	441.1	483.7	504.1	464.7	398.6	349.7
75°	219.0	230.0	247.3	278.8	327.7	349.7	376.5	392.3	356.0	311.9	282.0
77.5°	171.7	176.4	189.0	211.1	244.2	269.4	289.9	299.3	274.1	245.8	220.6
80°	121.3	127.6	137.1	156.0	181.2	189.0	201.7	212.7	196.9	171.7	156.0
82.5°	80.3	88.2	92.9	100.8	116.6	126.0	129.2	138.6	124.5	115.0	108.7
85°	47.3	50.4	52.0	56.7	64.6	69.3	74.0	75.6	72.5	70.9	64.6
87.5°	23.6	23.6	23.6	26.8	28.4	31.5	33.1	33.1	33.1	31.5	29.9
90°	1.1	2.3	3.4	5.1	6.3	6.8	7.4	9.1	10.9	12.6	14.3
92.5°	8.6	12.6	18.3	23.4	29.1	34.2	39.4	57.7	88.0	117.7	106.3
95°	19.4	21.1	27.4	37.1	52.0	63.2	74.3	122.9	208.0	301.7	338.9
97.5°	30.9	31.4	36.6	45.1	60.0	72.3	84.6	132.6	231.4	389.2	521.2
100°	42.3	42.9	46.9	54.9	68.6	79.8	90.9	130.9	215.4	365.7	541.2
102.5°	54.3	55.4	58.9	66.3	78.3	88.3	98.3	133.1	201.7	331.4	504.0
105°	66.3	68.0	71.4	78.3	89.1	98.0	106.9	137.7	196.6	304.6	459.4
107.5°	78.9	80.6	84.0	90.9	101.1	109.4	117.7	145.1	195.4	285.2	420.0
110°	92.6	94.3	97.1	103.4	113.1	121.1	129.1	154.9	198.3	274.9	387.4

TEST NUMBER: P1011381

CATALOG NUMBER: S123DIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	105.1	106.9	109.7	116.0	125.7	133.4	141.1	164.6	204.0	269.1	365.7
115°	117.1	119.4	122.9	128.6	138.3	146.0	153.7	175.4	210.3	268.6	351.4
117.5°	129.1	132.0	134.9	140.0	150.9	158.0	165.1	186.9	218.3	269.1	341.7
120°	141.7	143.4	146.3	152.0	162.9	170.0	177.1	197.7	227.4	271.4	335.4
122.5°	152.6	154.3	157.1	163.4	173.7	181.4	189.1	209.1	236.0	275.4	331.4
125°	162.9	164.0	167.4	173.7	184.6	192.3	200.0	220.0	245.1	279.4	328.0
127.5°	170.9	172.6	176.6	182.9	194.9	202.6	210.3	229.7	252.6	284.0	326.3
130°	178.3	180.0	185.1	192.0	204.0	211.7	219.4	238.3	260.0	288.6	324.6
132.5°	184.0	186.3	192.0	200.6	212.6	220.0	227.4	245.7	266.9	292.0	324.0
135°	190.9	193.1	199.4	208.0	220.0	227.7	235.4	253.1	272.6	295.4	323.4
137.5°	197.1	199.4	205.7	214.9	226.9	234.0	241.1	258.3	277.2	297.7	322.3
140°	203.4	206.3	212.0	221.1	232.6	239.8	246.9	263.4	280.6	300.0	321.7
142.5°	210.3	212.6	218.9	226.9	238.3	244.8	251.4	267.4	284.0	301.7	320.6
145°	217.7	219.4	224.6	233.1	242.9	249.4	256.0	270.9	286.3	302.3	319.4
147.5°	225.1	226.3	231.4	238.9	248.6	254.3	260.0	273.7	288.0	302.3	317.7
150°	232.6	233.1	237.7	245.1	253.1	258.2	263.4	276.6	288.6	302.3	315.4
152.5°	240.0	240.0	244.6	250.9	257.7	262.5	267.4	278.3	289.7	300.6	312.6
155°	247.4	247.4	250.9	256.6	262.9	266.9	270.9	280.6	289.7	299.4	309.2
157.5°	253.1	253.7	256.6	261.7	267.4	270.5	273.7	281.7	290.3	297.7	306.3
160°	260.0	260.0	262.3	266.9	270.9	273.8	276.6	283.4	290.3	296.6	302.9
162.5°	265.1	265.1	266.9	270.3	273.7	276.0	278.3	284.0	289.7	294.3	299.4
165°	270.3	269.7	270.9	273.7	276.0	278.0	280.0	284.6	288.6	292.0	296.0
167.5°	274.3	273.7	274.3	276.6	278.3	279.8	281.2	284.6	288.0	289.7	292.6
170°	277.7	276.6	277.2	278.9	280.0	280.6	281.2	284.0	286.3	287.4	289.2
172.5°	280.0	279.4	279.4	280.6	281.2	281.4	281.7	284.0	285.7	285.7	286.3
175°	281.7	281.2	280.6	281.7	281.7	282.0	282.3	283.4	284.6	284.0	284.0
177.5°	282.9	282.3	281.7	282.3	282.3	282.3	282.3	282.9	284.0	282.9	282.3
180°	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3

TEST NUMBER: P1011381

CATALOG NUMBER: S123DIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8
2.5°	1712.5	1715.6	1726.7	1734.5	1750.3	1748.7	1748.7	1747.1	1742.4	1750.3	1755.0
5°	1832.2	1859.0	1862.1	1896.8	1898.4	1912.5	1922.0	1914.1	1933.0	1931.5	1917.3
7.5°	1980.3	2016.5	2033.9	2066.9	2104.7	2095.3	2131.5	2137.8	2134.7	2150.4	2161.5
10°	2142.6	2205.6	2249.7	2311.1	2326.9	2336.3	2360.0	2380.4	2421.4	2389.9	2410.4
12.5°	2328.5	2374.1	2432.4	2530.1	2578.9	2610.5	2621.5	2635.7	2664.0	2646.7	2648.3
15°	2484.4	2545.9	2645.1	2766.4	2780.6	2820.0	2810.5	2895.6	2936.6	2875.1	2909.8
17.5°	2646.7	2728.6	2846.8	2952.3	3012.2	3039.0	3064.2	3146.1	3142.9	3133.5	3141.4
20°	2750.7	2884.6	3031.1	3171.3	3188.6	3209.1	3276.9	3311.5	3305.2	3332.0	3349.3
22.5°	2897.2	3039.0	3194.9	3287.9	3327.3	3350.9	3404.5	3426.5	3436.0	3442.3	3431.2
25°	3020.1	3171.3	3286.3	3368.2	3391.9	3404.5	3421.8	3428.1	3423.4	3412.3	3421.8
27.5°	3103.6	3224.9	3303.6	3341.4	3328.8	3308.4	3275.3	3253.2	3204.4	3180.8	3209.1
30°	3138.2	3191.8	3215.4	3152.4	3089.4	3039.0	2976.0	2859.4	2768.0	2794.8	2758.5
32.5°	3083.1	3048.4	2935.0	2772.7	2723.9	2642.0	2463.9	2326.9	2331.6	2259.1	2289.1
35°	2920.8	2763.3	2549.0	2303.3	2238.7	2194.5	1999.2	1969.3	1906.2	1838.5	1857.4
37.5°	2634.1	2404.1	2144.1	1963.0	1866.9	1770.8	1660.5	1594.3	1556.5	1528.1	1550.2
40°	2284.3	2003.9	1789.7	1627.4	1545.5	1484.0	1408.4	1342.3	1299.7	1295.0	1302.9
42.5°	1940.9	1704.6	1507.7	1353.3	1326.5	1254.0	1205.2	1153.2	1140.6	1120.1	1131.1
45°	1643.2	1451.0	1288.7	1162.7	1131.1	1112.2	1052.4	1019.3	1005.1	992.5	1011.4
47.5°	1427.3	1225.7	1107.5	1031.9	1000.4	968.9	935.8	913.7	902.7	904.3	902.7
50°	1219.4	1071.3	967.3	909.0	890.1	868.1	841.3	827.1	822.4	808.2	819.2
52.5°	1049.2	942.1	869.6	814.5	800.3	784.6	762.5	754.6	743.6	740.4	740.4
55°	912.2	828.7	770.4	734.1	716.8	704.2	691.6	682.2	674.3	674.3	674.3
57.5°	805.0	732.6	690.0	658.5	652.2	639.6	625.4	625.4	614.4	612.8	617.6
60°	713.7	649.1	616.0	589.2	579.8	576.6	562.4	562.4	559.3	551.4	557.7
62.5°	620.7	573.4	545.1	524.6	515.2	515.2	504.1	496.3	496.3	497.8	494.7
65°	535.6	501.0	475.8	460.0	455.3	449.0	447.4	441.1	436.4	438.0	436.4
67.5°	460.0	433.2	415.9	403.3	395.4	392.3	387.6	387.6	384.4	386.0	378.1
70°	392.3	365.5	351.3	338.7	335.6	335.6	329.3	330.8	327.7	332.4	329.3
72.5°	323.0	302.5	291.5	286.7	283.6	282.0	278.8	275.7	274.1	277.3	275.7
75°	261.5	244.2	236.3	233.2	230.0	230.0	228.4	226.9	225.3	225.3	225.3
77.5°	203.2	192.2	182.7	185.9	181.2	182.7	178.0	178.0	179.6	178.0	178.0
80°	149.7	141.8	141.8	138.6	132.3	135.5	135.5	130.8	129.2	132.3	127.6
82.5°	99.3	97.7	94.5	92.9	89.8	91.4	89.8	88.2	86.6	89.8	86.6
85°	58.3	58.3	56.7	53.6	56.7	55.1	53.6	53.6	52.0	52.0	52.0
87.5°	29.9	26.8	26.8	25.2	26.8	23.6	25.2	23.6	22.1	23.6	22.1
90°	13.7	14.3	14.9	15.4	16.0	16.6	16.0	16.6	17.1	16.6	17.1
92.5°	79.4	56.6	44.0	38.3	36.3	34.3	33.1	30.9	31.4	30.3	31.4
95°	274.9	205.7	139.4	109.1	98.8	88.6	77.7	72.6	68.6	66.3	68.6
97.5°	538.9	472.6	356.6	281.2	248.6	216.0	177.7	156.0	142.3	136.0	142.3
100°	653.7	673.7	627.4	560.6	520.0	479.4	421.7	380.0	357.7	358.3	357.7
102.5°	659.4	740.6	750.3	718.3	696.3	674.3	632.6	601.7	584.0	567.4	584.0
105°	623.4	742.9	800.0	810.9	803.4	796.0	769.7	748.0	729.7	726.9	729.7
107.5°	572.0	708.6	798.3	842.9	850.6	858.3	854.9	844.6	837.2	830.9	837.2
110°	524.0	654.9	760.0	832.0	852.0	872.0	888.0	892.6	891.5	890.3	891.5

TEST NUMBER: P1011381

CATALOG NUMBER: S123DIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	482.3	601.7	709.7	792.6	819.8	846.9	879.5	896.0	901.7	902.3	901.7
115°	450.3	556.0	655.4	739.4	770.6	801.7	844.6	869.7	881.2	884.0	881.2
117.5°	429.2	520.6	608.6	685.7	718.0	750.3	794.9	822.9	840.0	844.0	840.0
120°	413.2	493.7	570.9	639.4	668.3	697.2	742.3	774.3	788.0	791.4	788.0
122.5°	400.0	472.6	540.6	602.9	629.2	655.4	694.3	722.3	737.7	742.3	737.7
125°	389.2	454.3	516.6	571.4	594.3	617.2	653.7	678.9	693.2	697.2	693.2
127.5°	378.9	437.7	494.3	544.6	565.8	586.9	620.0	641.7	654.9	658.3	654.9
130°	370.9	422.3	473.7	520.0	539.4	558.9	589.2	609.7	621.7	626.3	621.7
132.5°	363.4	408.0	454.3	496.6	514.9	533.2	561.2	581.7	592.0	594.9	592.0
135°	357.2	395.4	436.0	473.2	489.4	505.7	533.7	550.9	561.2	565.2	561.2
137.5°	351.4	383.4	417.7	450.9	465.4	480.0	504.0	521.7	530.3	533.7	530.3
140°	346.3	373.2	402.3	429.7	442.0	454.3	476.0	492.0	501.2	500.6	501.2
142.5°	341.7	363.4	387.4	410.3	420.6	430.9	448.6	462.3	470.3	469.7	470.3
145°	337.7	356.0	374.9	393.2	401.4	409.7	424.0	436.0	440.6	441.7	440.6
147.5°	333.7	349.7	365.2	380.6	386.6	392.6	404.0	412.6	417.2	417.7	417.2
150°	329.7	342.9	356.0	368.0	373.4	378.9	387.4	393.7	397.2	397.2	397.2
152.5°	325.2	336.6	347.4	357.7	362.0	366.3	372.6	378.3	380.0	380.0	380.0
155°	320.6	330.3	339.4	348.0	351.4	354.9	360.0	364.6	365.7	366.3	365.7
157.5°	315.4	323.4	331.4	338.3	341.2	344.0	348.6	352.0	353.2	353.2	353.2
160°	310.3	317.7	324.0	329.7	331.7	333.7	337.7	341.2	341.2	340.6	341.2
162.5°	305.2	310.9	316.0	321.2	322.9	324.6	326.9	329.7	329.7	329.2	329.7
165°	300.6	305.2	308.6	312.6	314.0	315.4	317.7	320.0	319.4	319.4	319.4
167.5°	296.0	300.0	302.9	305.2	306.3	307.4	308.6	310.3	309.7	309.7	309.7
170°	292.0	294.9	296.6	298.9	299.4	300.0	300.6	301.7	301.2	301.2	301.2
172.5°	288.0	290.3	291.4	293.2	293.4	293.7	293.7	294.9	293.7	293.2	293.7
175°	285.2	286.3	286.9	288.0	288.0	288.0	288.0	288.6	288.0	287.4	288.0
177.5°	282.9	283.4	284.0	284.6	284.6	284.6	284.0	284.6	283.4	283.4	283.4
180°	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3

TEST NUMBER: P1011381

CATALOG NUMBER: S123DIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8
2.5°	1742.4	1747.1	1734.5	1731.4	1731.4	1737.7	1733.0	1690.4	1698.3	1688.8	1685.7
5°	1934.6	1925.2	1912.5	1906.2	1898.4	1876.3	1874.7	1825.9	1816.4	1784.9	1770.8
7.5°	2145.7	2137.8	2100.0	2095.3	2092.1	2071.7	2019.7	1967.7	1929.9	1893.6	1859.0
10°	2386.7	2363.1	2345.8	2311.1	2293.8	2265.4	2197.7	2148.9	2084.3	2029.1	1956.7
12.5°	2676.6	2649.8	2591.6	2566.3	2544.3	2465.5	2397.8	2342.6	2216.6	2178.8	2089.0
15°	2889.3	2832.6	2826.3	2771.1	2768.0	2681.4	2552.2	2492.3	2394.6	2256.0	2163.0
17.5°	3119.3	3068.9	3029.5	2963.3	2953.9	2872.0	2777.5	2630.9	2523.8	2391.5	2273.3
20°	3287.9	3261.1	3193.4	3166.6	3111.4	3042.1	2944.4	2763.3	2632.5	2500.2	2355.2
22.5°	3421.8	3395.0	3341.4	3305.2	3273.7	3183.9	3067.3	2912.9	2733.3	2560.0	2410.4
25°	3420.2	3412.3	3390.3	3373.0	3349.3	3283.2	3185.5	3037.4	2837.3	2646.7	2438.7
27.5°	3226.4	3248.5	3286.3	3305.2	3300.5	3291.0	3235.9	3111.4	2931.8	2705.0	2471.8
30°	2823.1	2903.5	2974.4	3068.9	3097.3	3166.6	3198.1	3127.2	2983.8	2772.7	2514.4
32.5°	2341.1	2457.6	2612.0	2664.0	2753.8	2887.7	3037.4	3064.2	2974.4	2812.1	2541.1
35°	1920.4	2016.5	2136.3	2218.2	2298.5	2515.9	2705.0	2868.8	2898.8	2791.6	2534.8
37.5°	1589.6	1657.3	1762.9	1832.2	1906.2	2092.1	2356.8	2569.5	2719.2	2722.3	2517.5
40°	1350.1	1380.1	1471.4	1521.8	1592.7	1753.4	1989.7	2267.0	2486.0	2586.8	2471.8
42.5°	1143.7	1183.1	1258.8	1296.6	1342.3	1482.5	1638.4	1901.5	2172.5	2388.3	2386.7
45°	1020.9	1049.2	1083.9	1115.4	1167.4	1250.9	1428.9	1625.8	1885.8	2130.0	2226.1
47.5°	912.2	938.9	973.6	983.1	1017.7	1096.5	1205.2	1376.9	1619.5	1862.1	2043.3
50°	820.8	842.8	866.5	883.8	899.6	964.2	1046.1	1191.0	1384.8	1619.5	1844.8
52.5°	749.9	765.6	786.1	795.6	809.8	857.0	920.0	1027.2	1186.3	1400.5	1619.5
55°	683.7	694.8	707.4	723.1	729.4	764.1	812.9	904.3	1022.4	1214.6	1422.6
57.5°	622.3	627.0	634.9	644.3	652.2	682.2	724.7	786.1	890.1	1038.2	1235.1
60°	553.0	565.6	570.3	579.8	584.5	608.1	641.2	693.2	773.5	901.1	1049.2
62.5°	494.7	502.6	510.4	515.2	526.2	534.1	560.8	608.1	674.3	768.8	902.7
65°	442.7	445.8	450.6	455.3	458.4	467.9	493.1	524.6	575.0	658.5	762.5
67.5°	382.8	386.0	392.3	393.9	397.0	409.6	423.8	450.6	493.1	556.1	641.2
70°	324.5	329.3	332.4	335.6	340.3	345.0	360.8	382.8	415.9	460.0	526.2
72.5°	274.1	278.8	278.8	282.0	280.4	286.7	302.5	318.2	340.3	376.5	434.8
75°	223.7	223.7	226.9	228.4	230.0	236.3	242.6	255.2	272.5	300.9	337.1
77.5°	176.4	174.9	178.0	178.0	178.0	182.7	189.0	195.4	206.4	226.9	255.2
80°	129.2	129.2	132.3	133.9	130.8	132.3	135.5	141.8	149.7	163.8	179.6
82.5°	85.1	91.4	89.8	91.4	89.8	92.9	94.5	96.1	99.3	105.6	116.6
85°	52.0	52.0	52.0	53.6	52.0	53.6	53.6	53.6	55.1	58.3	63.0
87.5°	22.1	22.1	22.1	23.6	22.1	22.1	23.6	22.1	23.6	23.6	25.2
90°	16.6	16.0	16.6	16.0	15.4	14.9	14.3	13.7	14.3	12.6	10.9
92.5°	30.9	33.1	34.3	36.3	38.3	44.0	56.6	79.4	106.3	117.7	88.0
95°	72.6	77.7	88.6	98.8	109.1	139.4	205.7	274.9	338.9	301.7	208.0
97.5°	156.0	177.7	216.0	248.6	281.2	356.6	472.6	538.9	521.2	389.2	231.4
100°	380.0	421.7	479.4	520.0	560.6	627.4	673.7	653.7	541.2	365.7	215.4
102.5°	601.7	632.6	674.3	696.3	718.3	750.3	740.6	659.4	504.0	331.4	201.7
105°	748.0	769.7	796.0	803.4	810.9	800.0	742.9	623.4	459.4	304.6	196.6
107.5°	844.6	854.9	858.3	850.6	842.9	798.3	708.6	572.0	420.0	285.2	195.4
110°	892.6	888.0	872.0	852.0	832.0	760.0	654.9	524.0	387.4	274.9	198.3

TEST NUMBER: P1011381

CATALOG NUMBER: S123DIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	896.0	879.5	846.9	819.8	792.6	709.7	601.7	482.3	365.7	269.1	204.0
115°	869.7	844.6	801.7	770.6	739.4	655.4	556.0	450.3	351.4	268.6	210.3
117.5°	822.9	794.9	750.3	718.0	685.7	608.6	520.6	429.2	341.7	269.1	218.3
120°	774.3	742.3	697.2	668.3	639.4	570.9	493.7	413.2	335.4	271.4	227.4
122.5°	722.3	694.3	655.4	629.2	602.9	540.6	472.6	400.0	331.4	275.4	236.0
125°	678.9	653.7	617.2	594.3	571.4	516.6	454.3	389.2	328.0	279.4	245.1
127.5°	641.7	620.0	586.9	565.8	544.6	494.3	437.7	378.9	326.3	284.0	252.6
130°	609.7	589.2	558.9	539.4	520.0	473.7	422.3	370.9	324.6	288.6	260.0
132.5°	581.7	561.2	533.2	514.9	496.6	454.3	408.0	363.4	324.0	292.0	266.9
135°	550.9	533.7	505.7	489.4	473.2	436.0	395.4	357.2	323.4	295.4	272.6
137.5°	521.7	504.0	480.0	465.4	450.9	417.7	383.4	351.4	322.3	297.7	277.2
140°	492.0	476.0	454.3	442.0	429.7	402.3	373.2	346.3	321.7	300.0	280.6
142.5°	462.3	448.6	430.9	420.6	410.3	387.4	363.4	341.7	320.6	301.7	284.0
145°	436.0	424.0	409.7	401.4	393.2	374.9	356.0	337.7	319.4	302.3	286.3
147.5°	412.6	404.0	392.6	386.6	380.6	365.2	349.7	333.7	317.7	302.3	288.0
150°	393.7	387.4	378.9	373.4	368.0	356.0	342.9	329.7	315.4	302.3	288.6
152.5°	378.3	372.6	366.3	362.0	357.7	347.4	336.6	325.2	312.6	300.6	289.7
155°	364.6	360.0	354.9	351.4	348.0	339.4	330.3	320.6	309.2	299.4	289.7
157.5°	352.0	348.6	344.0	341.2	338.3	331.4	323.4	315.4	306.3	297.7	290.3
160°	341.2	337.7	333.7	331.7	329.7	324.0	317.7	310.3	302.9	296.6	290.3
162.5°	329.7	326.9	324.6	322.9	321.2	316.0	310.9	305.2	299.4	294.3	289.7
165°	320.0	317.7	315.4	314.0	312.6	308.6	305.2	300.6	296.0	292.0	288.6
167.5°	310.3	308.6	307.4	306.3	305.2	302.9	300.0	296.0	292.6	289.7	288.0
170°	301.7	300.6	300.0	299.4	298.9	296.6	294.9	292.0	289.2	287.4	286.3
172.5°	294.9	293.7	293.7	293.4	293.2	291.4	290.3	288.0	286.3	285.7	285.7
175°	288.6	288.0	288.0	288.0	288.0	286.9	286.3	285.2	284.0	284.0	284.6
177.5°	284.6	284.0	284.6	284.6	284.6	284.0	283.4	282.9	282.3	282.9	284.0
180°	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3

TEST NUMBER: P1011381

CATALOG NUMBER: S123DIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8
2.5°	1669.9	1665.2	1665.2	1662.1	1652.6	1635.3	1633.7	1636.9	1627.4	1617.9	1603.8
5°	1751.9	1721.9	1712.5	1703.0	1684.1	1652.6	1640.0	1629.0	1611.6	1591.2	1569.1
7.5°	1821.2	1778.6	1766.0	1748.7	1710.9	1666.8	1638.4	1614.8	1591.2	1562.8	1536.0
10°	1907.8	1846.4	1816.4	1791.2	1739.3	1677.8	1635.3	1600.6	1562.8	1528.1	1493.5
12.5°	2005.5	1906.2	1896.8	1835.4	1775.5	1684.1	1632.1	1581.7	1531.3	1488.8	1452.5
15°	2087.4	1978.7	1939.3	1898.4	1783.4	1669.9	1619.5	1562.8	1504.5	1458.8	1405.3
17.5°	2139.4	2049.6	1966.1	1911.0	1791.2	1690.4	1592.7	1528.1	1466.7	1403.7	1359.6
20°	2202.4	2071.7	1999.2	1925.2	1807.0	1674.7	1577.0	1496.6	1421.0	1364.3	1310.7
22.5°	2265.4	2089.0	2029.1	1948.8	1810.1	1658.9	1548.6	1468.3	1381.6	1324.9	1266.6
25°	2259.1	2114.2	2015.0	1947.2	1778.6	1644.7	1515.5	1421.0	1340.7	1268.2	1209.9
27.5°	2263.9	2085.8	1985.0	1906.2	1756.6	1624.2	1480.9	1381.6	1298.1	1222.5	1161.1
30°	2265.4	2043.3	1955.1	1860.6	1715.6	1575.4	1441.5	1340.7	1252.5	1170.5	1115.4
32.5°	2260.7	2008.6	1898.4	1813.3	1651.0	1528.1	1395.8	1288.7	1198.9	1123.3	1071.3
35°	2249.7	1967.7	1840.1	1733.0	1584.9	1460.4	1353.3	1243.0	1146.9	1077.6	1017.7
37.5°	2219.8	1923.6	1778.6	1673.1	1507.7	1381.6	1287.1	1195.7	1102.8	1020.9	970.5
40°	2197.7	1863.7	1717.2	1602.2	1424.2	1301.3	1222.5	1135.9	1044.5	970.5	921.6
42.5°	2147.3	1807.0	1654.2	1517.1	1342.3	1216.2	1142.2	1072.9	994.1	921.6	877.5
45°	2065.4	1745.6	1577.0	1438.4	1252.5	1132.7	1065.0	1008.3	938.9	869.6	825.5
47.5°	1950.4	1657.3	1495.1	1356.4	1164.2	1042.9	975.2	932.6	877.5	819.2	781.4
50°	1825.9	1561.2	1411.6	1274.5	1079.2	961.0	894.8	855.4	819.2	765.6	729.4
52.5°	1663.6	1458.8	1315.5	1184.7	987.8	874.4	816.1	787.7	749.9	712.1	680.6
55°	1506.1	1326.5	1208.3	1083.9	898.0	792.4	735.7	705.8	683.7	652.2	627.0
57.5°	1323.3	1203.6	1094.9	981.5	814.5	718.4	664.8	628.6	614.4	600.2	576.6
60°	1154.8	1063.4	975.2	880.7	727.8	641.2	589.2	560.8	546.7	537.2	521.5
62.5°	1000.4	929.5	853.9	778.3	639.6	560.8	521.5	493.1	480.5	478.9	464.7
65°	852.3	801.9	740.4	666.4	557.7	488.4	450.6	433.2	419.1	419.1	408.0
67.5°	704.2	669.5	620.7	568.7	483.7	419.1	384.4	368.6	360.8	360.8	352.9
70°	586.1	562.4	518.3	472.6	398.6	349.7	323.0	308.8	304.1	305.6	299.3
72.5°	475.8	450.6	414.3	381.2	326.1	289.9	271.0	255.2	247.3	248.9	247.3
75°	368.6	356.0	324.5	299.3	255.2	230.0	212.7	204.8	198.5	200.1	196.9
77.5°	277.3	258.4	241.0	223.7	196.9	176.4	162.3	154.4	149.7	149.7	149.7
80°	189.0	185.9	171.7	162.3	140.2	124.5	113.4	111.9	107.1	107.1	107.1
82.5°	122.9	115.0	107.1	100.8	88.2	78.8	74.0	70.9	69.3	67.7	70.9
85°	67.7	63.0	59.9	53.6	48.8	44.1	39.4	37.8	36.2	37.8	36.2
87.5°	26.8	22.1	22.1	20.5	18.9	17.3	17.3	14.2	14.2	12.6	12.6
90°	9.1	7.4	6.8	6.3	5.1	3.4	2.3	1.1	2.3	3.4	5.1
92.5°	57.7	39.4	34.2	29.1	23.4	18.3	12.6	8.6	12.6	18.3	23.4
95°	122.9	74.3	63.2	52.0	37.1	27.4	21.1	19.4	21.1	27.4	37.1
97.5°	132.6	84.6	72.3	60.0	45.1	36.6	31.4	30.9	31.4	36.6	45.1
100°	130.9	90.9	79.8	68.6	54.9	46.9	42.9	42.3	42.9	46.9	54.9
102.5°	133.1	98.3	88.3	78.3	66.3	58.9	55.4	54.3	55.4	58.9	66.3
105°	137.7	106.9	98.0	89.1	78.3	71.4	68.0	66.3	68.0	71.4	78.3
107.5°	145.1	117.7	109.4	101.1	90.9	84.0	80.6	78.9	80.6	84.0	90.9
110°	154.9	129.1	121.1	113.1	103.4	97.1	94.3	92.6	94.3	97.1	103.4

TEST NUMBER: P1011381

CATALOG NUMBER: S123DIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	164.6	141.1	133.4	125.7	116.0	109.7	106.9	105.1	106.9	109.7	116.0
115°	175.4	153.7	146.0	138.3	128.6	122.9	119.4	117.1	119.4	122.9	128.6
117.5°	186.9	165.1	158.0	150.9	140.0	134.9	132.0	129.1	132.0	134.9	140.0
120°	197.7	177.1	170.0	162.9	152.0	146.3	143.4	141.7	143.4	146.3	152.0
122.5°	209.1	189.1	181.4	173.7	163.4	157.1	154.3	152.6	154.3	157.1	163.4
125°	220.0	200.0	192.3	184.6	173.7	167.4	164.0	162.9	164.0	167.4	173.7
127.5°	229.7	210.3	202.6	194.9	182.9	176.6	172.6	170.9	172.6	176.6	182.9
130°	238.3	219.4	211.7	204.0	192.0	185.1	180.0	178.3	180.0	185.1	192.0
132.5°	245.7	227.4	220.0	212.6	200.6	192.0	186.3	184.0	186.3	192.0	200.6
135°	253.1	235.4	227.7	220.0	208.0	199.4	193.1	190.9	193.1	199.4	208.0
137.5°	258.3	241.1	234.0	226.9	214.9	205.7	199.4	197.1	199.4	205.7	214.9
140°	263.4	246.9	239.8	232.6	221.1	212.0	206.3	203.4	206.3	212.0	221.1
142.5°	267.4	251.4	244.8	238.3	226.9	218.9	212.6	210.3	212.6	218.9	226.9
145°	270.9	256.0	249.4	242.9	233.1	224.6	219.4	217.7	219.4	224.6	233.1
147.5°	273.7	260.0	254.3	248.6	238.9	231.4	226.3	225.1	226.3	231.4	238.9
150°	276.6	263.4	258.2	253.1	245.1	237.7	233.1	232.6	233.1	237.7	245.1
152.5°	278.3	267.4	262.5	257.7	250.9	244.6	240.0	240.0	240.0	244.6	250.9
155°	280.6	270.9	266.9	262.9	256.6	250.9	247.4	247.4	247.4	250.9	256.6
157.5°	281.7	273.7	270.5	267.4	261.7	256.6	253.7	253.1	253.7	256.6	261.7
160°	283.4	276.6	273.8	270.9	266.9	262.3	260.0	260.0	260.0	262.3	266.9
162.5°	284.0	278.3	276.0	273.7	270.3	266.9	265.1	265.1	265.1	266.9	270.3
165°	284.6	280.0	278.0	276.0	273.7	270.9	269.7	270.3	269.7	270.9	273.7
167.5°	284.6	281.2	279.8	278.3	276.6	274.3	273.7	274.3	273.7	274.3	276.6
170°	284.0	281.2	280.6	280.0	278.9	277.2	276.6	277.7	276.6	277.2	278.9
172.5°	284.0	281.7	281.4	281.2	280.6	279.4	279.4	280.0	279.4	279.4	280.6
175°	283.4	282.3	282.0	281.7	281.7	280.6	281.2	281.7	281.2	280.6	281.7
177.5°	282.9	282.3	282.3	282.3	282.3	281.7	282.3	282.9	282.3	281.7	282.3
180°	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3

TEST NUMBER: P1011381

CATALOG NUMBER: S123DIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8
2.5°	1600.6	1599.0	1602.2	1592.7	1577.0	1569.1	1547.1	1542.3	1540.8	1542.3	1543.9
5°	1556.5	1554.9	1550.2	1534.5	1515.5	1501.4	1474.6	1473.0	1463.6	1454.1	1458.8
7.5°	1514.0	1507.7	1498.2	1477.7	1452.5	1436.8	1414.7	1399.0	1386.4	1378.5	1372.2
10°	1471.4	1462.0	1452.5	1425.7	1394.2	1370.6	1343.8	1331.2	1317.0	1310.7	1304.4
12.5°	1416.3	1406.8	1389.5	1358.0	1339.1	1309.2	1282.4	1269.8	1261.9	1249.3	1241.4
15°	1372.2	1353.3	1343.8	1310.7	1271.4	1268.2	1219.4	1216.2	1200.5	1200.5	1187.9
17.5°	1321.8	1307.6	1290.3	1257.2	1228.8	1200.5	1175.3	1165.8	1151.6	1148.5	1142.2
20°	1272.9	1254.0	1247.7	1214.6	1184.7	1150.1	1123.3	1113.8	1107.5	1101.2	1105.9
22.5°	1222.5	1206.8	1191.0	1161.1	1139.0	1104.4	1088.6	1079.2	1069.7	1066.6	1068.1
25°	1173.7	1159.5	1143.7	1113.8	1090.2	1061.8	1047.6	1042.9	1038.2	1038.2	1036.6
27.5°	1126.4	1112.2	1098.1	1071.3	1047.6	1027.2	1016.1	1011.4	1006.7	1009.8	1013.0
30°	1077.6	1065.0	1052.4	1028.7	1009.8	990.9	984.6	981.5	979.9	987.8	987.8
32.5°	1033.5	1022.4	1013.0	990.9	972.0	956.3	951.5	953.1	954.7	959.4	962.6
35°	987.8	979.9	970.5	951.5	935.8	921.6	923.2	923.2	926.3	934.2	940.5
37.5°	946.8	935.8	927.9	912.2	899.6	887.0	891.7	896.4	899.6	909.0	912.2
40°	898.0	893.3	887.0	871.2	860.2	858.6	860.2	863.3	869.6	874.4	879.1
42.5°	858.6	852.3	844.4	831.8	822.4	823.9	825.5	828.7	831.8	839.7	844.4
45°	814.5	809.8	803.5	792.4	784.6	786.1	787.7	787.7	790.9	800.3	803.5
47.5°	765.6	767.2	759.3	748.3	743.6	743.6	743.6	746.7	754.6	757.8	759.3
50°	718.4	715.2	713.7	702.6	699.5	697.9	699.5	701.1	712.1	710.5	715.2
52.5°	668.0	668.0	666.4	660.1	655.4	655.4	652.2	660.1	663.2	666.4	671.1
55°	619.1	614.4	612.8	609.7	603.4	601.8	605.0	614.4	617.6	620.7	625.4
57.5°	565.6	565.6	562.4	557.7	557.7	557.7	557.7	564.0	568.7	571.9	581.3
60°	516.7	510.4	505.7	505.7	505.7	504.1	513.6	513.6	523.0	524.6	527.8
62.5°	458.4	455.3	452.1	453.7	452.1	455.3	458.4	464.7	466.3	471.0	475.8
65°	403.3	403.3	400.2	409.6	403.3	403.3	411.2	411.2	414.3	419.1	425.4
67.5°	349.7	351.3	348.2	348.2	351.3	352.9	354.5	360.8	362.3	368.6	376.5
70°	294.6	297.8	299.3	296.2	299.3	302.5	305.6	307.2	313.5	316.7	321.4
72.5°	245.8	248.9	244.2	245.8	247.3	250.5	252.1	255.2	258.4	267.8	271.0
75°	196.9	195.4	193.8	200.1	196.9	203.2	204.8	204.8	208.0	215.8	219.0
77.5°	151.2	151.2	152.8	149.7	154.4	152.8	154.4	159.1	163.8	163.8	176.4
80°	105.6	108.7	108.7	108.7	110.3	111.9	108.7	116.6	118.2	118.2	122.9
82.5°	67.7	69.3	67.7	70.9	70.9	74.0	72.5	74.0	77.2	80.3	81.9
85°	36.2	36.2	39.4	39.4	37.8	39.4	37.8	39.4	42.5	42.5	44.1
87.5°	12.6	12.6	12.6	12.6	14.2	12.6	14.2	14.2	12.6	12.6	17.3
90°	6.3	6.8	7.4	9.1	10.9	12.6	14.3	13.7	14.3	14.9	15.4
92.5°	29.1	34.2	39.4	57.7	88.0	117.7	106.3	79.4	56.6	44.0	38.3
95°	52.0	63.2	74.3	122.9	208.0	301.7	338.9	274.9	205.7	139.4	109.1
97.5°	60.0	72.3	84.6	132.6	231.4	389.2	521.2	538.9	472.6	356.6	281.2
100°	68.6	79.8	90.9	130.9	215.4	365.7	541.2	653.7	673.7	627.4	560.6
102.5°	78.3	88.3	98.3	133.1	201.7	331.4	504.0	659.4	740.6	750.3	718.3
105°	89.1	98.0	106.9	137.7	196.6	304.6	459.4	623.4	742.9	800.0	810.9
107.5°	101.1	109.4	117.7	145.1	195.4	285.2	420.0	572.0	708.6	798.3	842.9
110°	113.1	121.1	129.1	154.9	198.3	274.9	387.4	524.0	654.9	760.0	832.0

TEST NUMBER: P1011381

CATALOG NUMBER: S123DIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	125.7	133.4	141.1	164.6	204.0	269.1	365.7	482.3	601.7	709.7	792.6
115°	138.3	146.0	153.7	175.4	210.3	268.6	351.4	450.3	556.0	655.4	739.4
117.5°	150.9	158.0	165.1	186.9	218.3	269.1	341.7	429.2	520.6	608.6	685.7
120°	162.9	170.0	177.1	197.7	227.4	271.4	335.4	413.2	493.7	570.9	639.4
122.5°	173.7	181.4	189.1	209.1	236.0	275.4	331.4	400.0	472.6	540.6	602.9
125°	184.6	192.3	200.0	220.0	245.1	279.4	328.0	389.2	454.3	516.6	571.4
127.5°	194.9	202.6	210.3	229.7	252.6	284.0	326.3	378.9	437.7	494.3	544.6
130°	204.0	211.7	219.4	238.3	260.0	288.6	324.6	370.9	422.3	473.7	520.0
132.5°	212.6	220.0	227.4	245.7	266.9	292.0	324.0	363.4	408.0	454.3	496.6
135°	220.0	227.7	235.4	253.1	272.6	295.4	323.4	357.2	395.4	436.0	473.2
137.5°	226.9	234.0	241.1	258.3	277.2	297.7	322.3	351.4	383.4	417.7	450.9
140°	232.6	239.8	246.9	263.4	280.6	300.0	321.7	346.3	373.2	402.3	429.7
142.5°	238.3	244.8	251.4	267.4	284.0	301.7	320.6	341.7	363.4	387.4	410.3
145°	242.9	249.4	256.0	270.9	286.3	302.3	319.4	337.7	356.0	374.9	393.2
147.5°	248.6	254.3	260.0	273.7	288.0	302.3	317.7	333.7	349.7	365.2	380.6
150°	253.1	258.2	263.4	276.6	288.6	302.3	315.4	329.7	342.9	356.0	368.0
152.5°	257.7	262.5	267.4	278.3	289.7	300.6	312.6	325.2	336.6	347.4	357.7
155°	262.9	266.9	270.9	280.6	289.7	299.4	309.2	320.6	330.3	339.4	348.0
157.5°	267.4	270.5	273.7	281.7	290.3	297.7	306.3	315.4	323.4	331.4	338.3
160°	270.9	273.8	276.6	283.4	290.3	296.6	302.9	310.3	317.7	324.0	329.7
162.5°	273.7	276.0	278.3	284.0	289.7	294.3	299.4	305.2	310.9	316.0	321.2
165°	276.0	278.0	280.0	284.6	288.6	292.0	296.0	300.6	305.2	308.6	312.6
167.5°	278.3	279.8	281.2	284.6	288.0	289.7	292.6	296.0	300.0	302.9	305.2
170°	280.0	280.6	281.2	284.0	286.3	287.4	289.2	292.0	294.9	296.6	298.9
172.5°	281.2	281.4	281.7	284.0	285.7	285.7	286.3	288.0	290.3	291.4	293.2
175°	281.7	282.0	282.3	283.4	284.6	284.0	284.0	285.2	286.3	286.9	288.0
177.5°	282.3	282.3	282.3	282.9	284.0	282.9	282.3	282.9	283.4	284.0	284.6
180°	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3

TEST NUMBER: P1011381

CATALOG NUMBER: S123DIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8
2.5°	1542.3	1543.9	1537.6	1532.9	1545.5	1537.6	1537.6	1539.2	1536.0	1540.8	1539.2
5°	1455.7	1457.3	1446.2	1449.4	1443.1	1441.5	1439.9	1449.4	1447.8	1446.2	1449.4
7.5°	1370.6	1370.6	1365.9	1362.7	1362.7	1358.0	1364.3	1362.7	1365.9	1365.9	1370.6
10°	1299.7	1302.9	1295.0	1287.1	1285.5	1287.1	1287.1	1288.7	1290.3	1301.3	1299.7
12.5°	1241.4	1236.7	1235.1	1230.4	1222.5	1219.4	1216.2	1233.5	1228.8	1228.8	1228.8
15°	1176.8	1187.9	1186.3	1172.1	1169.0	1175.3	1172.1	1172.1	1187.9	1186.3	1184.7
17.5°	1142.2	1139.0	1135.9	1128.0	1129.6	1128.0	1129.6	1129.6	1139.0	1139.0	1139.0
20°	1102.8	1096.5	1096.5	1093.3	1093.3	1088.6	1094.9	1096.5	1102.8	1102.8	1104.4
22.5°	1068.1	1063.4	1063.4	1061.8	1065.0	1058.7	1065.0	1066.6	1066.6	1071.3	1071.3
25°	1038.2	1035.0	1035.0	1038.2	1038.2	1038.2	1038.2	1044.5	1039.8	1041.3	1039.8
27.5°	1011.4	1013.0	1014.6	1016.1	1014.6	1016.1	1017.7	1020.9	1022.4	1020.9	1017.7
30°	986.2	990.9	992.5	992.5	995.7	997.2	998.8	998.8	1000.4	995.7	998.8
32.5°	967.3	967.3	970.5	972.0	975.2	976.8	976.8	979.9	978.3	973.6	975.2
35°	940.5	940.5	946.8	950.0	954.7	953.1	954.7	954.7	956.3	953.1	948.4
37.5°	913.7	916.9	916.9	923.2	924.8	926.3	924.8	927.9	926.3	923.2	921.6
40°	882.2	880.7	882.2	887.0	888.5	888.5	888.5	891.7	891.7	891.7	890.1
42.5°	842.8	847.6	846.0	850.7	849.1	849.1	852.3	855.4	857.0	852.3	853.9
45°	805.0	805.0	808.2	808.2	809.8	809.8	816.1	812.9	816.1	812.9	814.5
47.5°	764.1	765.6	765.6	767.2	770.4	773.5	770.4	772.0	772.0	773.5	770.4
50°	718.4	718.4	721.5	726.3	732.6	729.4	727.8	734.1	729.4	729.4	726.3
52.5°	671.1	675.9	677.4	682.2	686.9	688.5	690.0	686.9	688.5	683.7	685.3
55°	625.4	627.0	633.3	638.0	642.8	642.8	641.2	642.8	644.3	638.0	638.0
57.5°	579.8	584.5	590.8	590.8	597.1	597.1	595.5	595.5	597.1	592.4	590.8
60°	530.9	535.6	543.5	543.5	553.0	554.5	551.4	548.2	548.2	543.5	545.1
62.5°	478.9	483.7	488.4	496.3	502.6	499.4	505.7	499.4	501.0	491.5	491.5
65°	433.2	434.8	442.7	450.6	450.6	453.7	450.6	452.1	447.4	447.4	441.1
67.5°	379.7	379.7	387.6	395.4	403.3	403.3	403.3	398.6	398.6	393.9	393.9
70°	332.4	330.8	338.7	343.4	348.2	349.7	346.6	345.0	341.9	337.1	335.6
72.5°	274.1	277.3	285.1	288.3	296.2	294.6	302.5	293.0	293.0	285.1	283.6
75°	222.1	225.3	233.2	237.9	242.6	242.6	247.3	242.6	236.3	233.2	231.6
77.5°	176.4	174.9	181.2	189.0	190.6	189.0	192.2	190.6	184.3	184.3	181.2
80°	126.0	130.8	137.1	135.5	141.8	140.2	140.2	137.1	137.1	132.3	135.5
82.5°	83.5	88.2	89.8	88.2	89.8	92.9	94.5	92.9	92.9	89.8	91.4
85°	44.1	44.1	47.3	48.8	47.3	47.3	48.8	53.6	50.4	47.3	50.4
87.5°	14.2	12.6	12.6	14.2	12.6	12.6	14.2	14.2	15.8	15.8	15.8
90°	16.0	16.6	16.0	16.6	17.1	16.6	17.1	16.6	16.0	16.6	16.0
92.5°	36.3	34.3	33.1	30.9	31.4	30.3	31.4	30.9	33.1	34.3	36.3
95°	98.8	88.6	77.7	72.6	68.6	66.3	68.6	72.6	77.7	88.6	98.8
97.5°	248.6	216.0	177.7	156.0	142.3	136.0	142.3	156.0	177.7	216.0	248.6
100°	520.0	479.4	421.7	380.0	357.7	358.3	357.7	380.0	421.7	479.4	520.0
102.5°	696.3	674.3	632.6	601.7	584.0	567.4	584.0	601.7	632.6	674.3	696.3
105°	803.4	796.0	769.7	748.0	729.7	726.9	729.7	748.0	769.7	796.0	803.4
107.5°	850.6	858.3	854.9	844.6	837.2	830.9	837.2	844.6	854.9	858.3	850.6
110°	852.0	872.0	888.0	892.6	891.5	890.3	891.5	892.6	888.0	872.0	852.0

TEST NUMBER: P1011381

CATALOG NUMBER: S123DIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	819.8	846.9	879.5	896.0	901.7	902.3	901.7	896.0	879.5	846.9	819.8
115°	770.6	801.7	844.6	869.7	881.2	884.0	881.2	869.7	844.6	801.7	770.6
117.5°	718.0	750.3	794.9	822.9	840.0	844.0	840.0	822.9	794.9	750.3	718.0
120°	668.3	697.2	742.3	774.3	788.0	791.4	788.0	774.3	742.3	697.2	668.3
122.5°	629.2	655.4	694.3	722.3	737.7	742.3	737.7	722.3	694.3	655.4	629.2
125°	594.3	617.2	653.7	678.9	693.2	697.2	693.2	678.9	653.7	617.2	594.3
127.5°	565.8	586.9	620.0	641.7	654.9	658.3	654.9	641.7	620.0	586.9	565.8
130°	539.4	558.9	589.2	609.7	621.7	626.3	621.7	609.7	589.2	558.9	539.4
132.5°	514.9	533.2	561.2	581.7	592.0	594.9	592.0	581.7	561.2	533.2	514.9
135°	489.4	505.7	533.7	550.9	561.2	565.2	561.2	550.9	533.7	505.7	489.4
137.5°	465.4	480.0	504.0	521.7	530.3	533.7	530.3	521.7	504.0	480.0	465.4
140°	442.0	454.3	476.0	492.0	501.2	500.6	501.2	492.0	476.0	454.3	442.0
142.5°	420.6	430.9	448.6	462.3	470.3	469.7	470.3	462.3	448.6	430.9	420.6
145°	401.4	409.7	424.0	436.0	440.6	441.7	440.6	436.0	424.0	409.7	401.4
147.5°	386.6	392.6	404.0	412.6	417.2	417.7	417.2	412.6	404.0	392.6	386.6
150°	373.4	378.9	387.4	393.7	397.2	397.2	397.2	393.7	387.4	378.9	373.4
152.5°	362.0	366.3	372.6	378.3	380.0	380.0	380.0	378.3	372.6	366.3	362.0
155°	351.4	354.9	360.0	364.6	365.7	366.3	365.7	364.6	360.0	354.9	351.4
157.5°	341.2	344.0	348.6	352.0	353.2	353.2	353.2	352.0	348.6	344.0	341.2
160°	331.7	333.7	337.7	341.2	341.2	340.6	341.2	341.2	337.7	333.7	331.7
162.5°	322.9	324.6	326.9	329.7	329.7	329.2	329.7	329.7	326.9	324.6	322.9
165°	314.0	315.4	317.7	320.0	319.4	319.4	319.4	320.0	317.7	315.4	314.0
167.5°	306.3	307.4	308.6	310.3	309.7	309.7	309.7	310.3	308.6	307.4	306.3
170°	299.4	300.0	300.6	301.7	301.2	301.2	301.2	301.7	300.6	300.0	299.4
172.5°	293.4	293.7	293.7	294.9	293.7	293.2	293.7	294.9	293.7	293.7	293.4
175°	288.0	288.0	288.0	288.6	288.0	287.4	288.0	288.6	288.0	288.0	288.0
177.5°	284.6	284.6	284.0	284.6	283.4	283.4	283.4	284.6	284.0	284.6	284.6
180°	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3

TEST NUMBER: P1011381

CATALOG NUMBER: S123DIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8	1625.8
2.5°	1543.9	1547.1	1548.6	1542.3	1537.6	1545.5	1556.5	1564.4	1570.7	1578.6	1583.3
5°	1452.5	1463.6	1463.6	1466.7	1471.4	1479.3	1499.8	1514.0	1526.6	1536.0	1543.9
7.5°	1375.3	1383.2	1387.9	1395.8	1403.7	1414.7	1438.4	1458.8	1477.7	1488.8	1501.4
10°	1306.0	1312.3	1320.2	1324.9	1339.1	1354.9	1384.8	1402.1	1424.2	1441.5	1457.3
12.5°	1239.8	1261.9	1266.6	1265.1	1277.7	1295.0	1324.9	1351.7	1375.3	1392.7	1410.0
15°	1192.6	1200.5	1209.9	1208.3	1235.1	1239.8	1265.1	1296.6	1328.1	1339.1	1354.9
17.5°	1140.6	1153.2	1162.7	1167.4	1175.3	1192.6	1216.2	1239.8	1280.8	1282.4	1323.3
20°	1099.6	1112.2	1118.5	1124.8	1129.6	1150.1	1170.5	1197.3	1230.4	1247.7	1269.8
22.5°	1072.9	1079.2	1083.9	1088.6	1094.9	1105.9	1131.1	1161.1	1183.1	1202.0	1216.2
25°	1041.3	1047.6	1054.0	1057.1	1061.8	1068.1	1087.0	1110.7	1142.2	1154.8	1169.0
27.5°	1019.3	1019.3	1022.4	1022.4	1028.7	1035.0	1049.2	1071.3	1096.5	1112.2	1131.1
30°	995.7	994.1	995.7	994.1	992.5	1002.0	1014.6	1033.5	1050.8	1069.7	1082.3
32.5°	972.0	970.5	970.5	972.0	965.7	970.5	976.8	994.1	1013.0	1022.4	1036.6
35°	946.8	943.7	943.7	943.7	940.5	937.4	943.7	959.4	972.0	984.6	995.7
37.5°	921.6	916.9	916.9	913.7	910.6	905.9	905.9	918.5	935.8	940.5	954.7
40°	887.0	887.0	883.8	882.2	879.1	875.9	871.2	882.2	898.0	902.7	913.7
42.5°	852.3	847.6	846.0	846.0	846.0	841.3	838.1	846.0	855.4	863.3	869.6
45°	812.9	809.8	811.3	809.8	806.6	805.0	803.5	806.6	817.6	820.8	828.7
47.5°	770.4	768.8	768.8	767.2	765.6	767.2	760.9	768.8	772.0	775.1	781.4
50°	726.3	724.7	723.1	721.5	721.5	723.1	721.5	721.5	727.8	731.0	737.3
52.5°	682.2	677.4	677.4	675.9	675.9	672.7	675.9	677.4	680.6	683.7	686.9
55°	634.9	634.9	630.2	630.2	627.0	627.0	628.6	627.0	633.3	636.5	636.5
57.5°	589.2	582.9	584.5	581.3	578.2	576.6	576.6	579.8	582.9	582.9	586.1
60°	540.4	534.1	532.5	526.2	529.3	524.6	526.2	526.2	532.5	529.3	532.5
62.5°	491.5	483.7	478.9	475.8	475.8	477.3	474.2	472.6	475.8	478.9	485.2
65°	439.5	434.8	430.1	425.4	425.4	423.8	426.9	422.2	420.6	422.2	425.4
67.5°	386.0	381.2	376.5	371.8	373.4	368.6	365.5	370.2	367.1	368.6	371.8
70°	334.0	330.8	321.4	318.2	316.7	318.2	316.7	313.5	318.2	316.7	318.2
72.5°	282.0	278.8	274.1	266.2	266.2	264.7	263.1	263.1	261.5	261.5	261.5
75°	231.6	225.3	220.6	219.0	215.8	214.3	212.7	209.5	211.1	212.7	209.5
77.5°	179.6	171.7	170.1	170.1	165.4	165.4	167.0	165.4	163.8	163.8	163.8
80°	132.3	126.0	126.0	122.9	119.7	119.7	119.7	119.7	118.2	116.6	118.2
82.5°	85.1	83.5	81.9	81.9	85.1	78.8	81.9	80.3	78.8	78.8	77.2
85°	47.3	48.8	47.3	48.8	45.7	47.3	47.3	47.3	45.7	47.3	44.1
87.5°	17.3	17.3	17.3	18.9	18.9	18.9	18.9	18.9	20.5	18.9	18.9
90°	15.4	14.9	14.3	13.7	14.3	12.6	10.9	9.1	7.4	6.8	6.3
92.5°	38.3	44.0	56.6	79.4	106.3	117.7	88.0	57.7	39.4	34.2	29.1
95°	109.1	139.4	205.7	274.9	338.9	301.7	208.0	122.9	74.3	63.2	52.0
97.5°	281.2	356.6	472.6	538.9	521.2	389.2	231.4	132.6	84.6	72.3	60.0
100°	560.6	627.4	673.7	653.7	541.2	365.7	215.4	130.9	90.9	79.8	68.6
102.5°	718.3	750.3	740.6	659.4	504.0	331.4	201.7	133.1	98.3	88.3	78.3
105°	810.9	800.0	742.9	623.4	459.4	304.6	196.6	137.7	106.9	98.0	89.1
107.5°	842.9	798.3	708.6	572.0	420.0	285.2	195.4	145.1	117.7	109.4	101.1
110°	832.0	760.0	654.9	524.0	387.4	274.9	198.3	154.9	129.1	121.1	113.1

TEST NUMBER: P1011381

CATALOG NUMBER: S123DIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	792.6	709.7	601.7	482.3	365.7	269.1	204.0	164.6	141.1	133.4	125.7
115°	739.4	655.4	556.0	450.3	351.4	268.6	210.3	175.4	153.7	146.0	138.3
117.5°	685.7	608.6	520.6	429.2	341.7	269.1	218.3	186.9	165.1	158.0	150.9
120°	639.4	570.9	493.7	413.2	335.4	271.4	227.4	197.7	177.1	170.0	162.9
122.5°	602.9	540.6	472.6	400.0	331.4	275.4	236.0	209.1	189.1	181.4	173.7
125°	571.4	516.6	454.3	389.2	328.0	279.4	245.1	220.0	200.0	192.3	184.6
127.5°	544.6	494.3	437.7	378.9	326.3	284.0	252.6	229.7	210.3	202.6	194.9
130°	520.0	473.7	422.3	370.9	324.6	288.6	260.0	238.3	219.4	211.7	204.0
132.5°	496.6	454.3	408.0	363.4	324.0	292.0	266.9	245.7	227.4	220.0	212.6
135°	473.2	436.0	395.4	357.2	323.4	295.4	272.6	253.1	235.4	227.7	220.0
137.5°	450.9	417.7	383.4	351.4	322.3	297.7	277.2	258.3	241.1	234.0	226.9
140°	429.7	402.3	373.2	346.3	321.7	300.0	280.6	263.4	246.9	239.8	232.6
142.5°	410.3	387.4	363.4	341.7	320.6	301.7	284.0	267.4	251.4	244.8	238.3
145°	393.2	374.9	356.0	337.7	319.4	302.3	286.3	270.9	256.0	249.4	242.9
147.5°	380.6	365.2	349.7	333.7	317.7	302.3	288.0	273.7	260.0	254.3	248.6
150°	368.0	356.0	342.9	329.7	315.4	302.3	288.6	276.6	263.4	258.2	253.1
152.5°	357.7	347.4	336.6	325.2	312.6	300.6	289.7	278.3	267.4	262.5	257.7
155°	348.0	339.4	330.3	320.6	309.2	299.4	289.7	280.6	270.9	266.9	262.9
157.5°	338.3	331.4	323.4	315.4	306.3	297.7	290.3	281.7	273.7	270.5	267.4
160°	329.7	324.0	317.7	310.3	302.9	296.6	290.3	283.4	276.6	273.8	270.9
162.5°	321.2	316.0	310.9	305.2	299.4	294.3	289.7	284.0	278.3	276.0	273.7
165°	312.6	308.6	305.2	300.6	296.0	292.0	288.6	284.6	280.0	278.0	276.0
167.5°	305.2	302.9	300.0	296.0	292.6	289.7	288.0	284.6	281.2	279.8	278.3
170°	298.9	296.6	294.9	292.0	289.2	287.4	286.3	284.0	281.2	280.6	280.0
172.5°	293.2	291.4	290.3	288.0	286.3	285.7	285.7	284.0	281.7	281.4	281.2
175°	288.0	286.9	286.3	285.2	284.0	284.0	284.6	283.4	282.3	282.0	281.7
177.5°	284.6	284.0	283.4	282.9	282.3	282.9	284.0	282.9	282.3	282.3	282.3
180°	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3

TEST NUMBER: P1011381

CATALOG NUMBER: S123DIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1625.8	1625.8	1625.8	1625.8
2.5°	1591.2	1595.9	1611.6	1630.6
5°	1559.7	1572.3	1594.3	1624.2
7.5°	1525.0	1543.9	1575.4	1613.2
10°	1485.6	1512.4	1551.8	1599.0
12.5°	1443.1	1477.7	1528.1	1577.0
15°	1416.3	1451.0	1496.6	1550.2
17.5°	1364.3	1405.3	1452.5	1528.1
20°	1310.7	1356.4	1417.9	1493.5
22.5°	1269.8	1318.6	1376.9	1457.3
25°	1220.9	1271.4	1334.4	1417.9
27.5°	1169.0	1219.4	1290.3	1378.5
30°	1129.6	1178.4	1246.2	1340.7
32.5°	1082.3	1129.6	1200.5	1299.7
35°	1028.7	1082.3	1150.1	1250.9
37.5°	987.8	1036.6	1107.5	1203.6
40°	943.7	986.2	1055.5	1150.1
42.5°	896.4	943.7	1003.5	1098.1
45°	852.3	887.0	948.4	1038.2
47.5°	805.0	844.4	891.7	961.0
50°	754.6	787.7	839.7	887.0
52.5°	705.8	732.6	776.7	812.9
55°	653.8	680.6	713.7	735.7
57.5°	605.0	623.9	645.9	660.1
60°	545.1	564.0	578.2	592.4
62.5°	491.5	505.7	513.6	521.5
65°	436.4	444.3	449.0	455.3
67.5°	376.5	384.4	386.0	395.4
70°	321.4	323.0	326.1	330.8
72.5°	269.4	272.5	271.0	274.1
75°	215.8	219.0	215.8	219.0
77.5°	163.8	167.0	167.0	171.7
80°	118.2	119.7	121.3	121.3
82.5°	77.2	81.9	78.8	80.3
85°	44.1	45.7	45.7	47.3
87.5°	20.5	22.1	20.5	23.6
90°	5.1	3.4	2.3	1.1
92.5°	23.4	18.3	12.6	8.6
95°	37.1	27.4	21.1	19.4
97.5°	45.1	36.6	31.4	30.9
100°	54.9	46.9	42.9	42.3
102.5°	66.3	58.9	55.4	54.3
105°	78.3	71.4	68.0	66.3
107.5°	90.9	84.0	80.6	78.9
110°	103.4	97.1	94.3	92.6

TEST NUMBER: P1011381

CATALOG NUMBER: S123DIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	116.0	109.7	106.9	105.1
115°	128.6	122.9	119.4	117.1
117.5°	140.0	134.9	132.0	129.1
120°	152.0	146.3	143.4	141.7
122.5°	163.4	157.1	154.3	152.6
125°	173.7	167.4	164.0	162.9
127.5°	182.9	176.6	172.6	170.9
130°	192.0	185.1	180.0	178.3
132.5°	200.6	192.0	186.3	184.0
135°	208.0	199.4	193.1	190.9
137.5°	214.9	205.7	199.4	197.1
140°	221.1	212.0	206.3	203.4
142.5°	226.9	218.9	212.6	210.3
145°	233.1	224.6	219.4	217.7
147.5°	238.9	231.4	226.3	225.1
150°	245.1	237.7	233.1	232.6
152.5°	250.9	244.6	240.0	240.0
155°	256.6	250.9	247.4	247.4
157.5°	261.7	256.6	253.7	253.1
160°	266.9	262.3	260.0	260.0
162.5°	270.3	266.9	265.1	265.1
165°	273.7	270.9	269.7	270.3
167.5°	276.6	274.3	273.7	274.3
170°	278.9	277.2	276.6	277.7
172.5°	280.6	279.4	279.4	280.0
175°	281.7	280.6	281.2	281.7
177.5°	282.3	281.7	282.3	282.9
180°	282.3	282.3	282.3	282.3

(END OF REPORT)