

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011390

Luminaire Tested: S123DIP-B1165D585UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011390
REPORT IS A COMBINATION OF REPORTS P989534 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1165D585UB35-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7062.0 lumens
Efficiency: N/A
Efficacy: 92.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011390

CATALOG NUMBER: S123DIP-B1165D585UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1011390

CATALOG NUMBER: S123DIP-B1165D585UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74
1	103	98	94	91	97	93	90	87	83	81	79	75	73	71	66	65	64
2	94	86	80	75	88	82	76	72	74	69	66	66	63	60	59	56	54
3	86	76	69	63	81	72	66	60	65	60	56	59	54	51	52	49	46
4	79	68	60	54	74	64	57	52	58	52	48	52	48	44	47	43	40
5	72	61	52	46	68	58	50	45	52	46	41	47	42	38	43	39	35
6	67	55	46	40	63	52	44	39	47	41	36	43	38	34	39	34	31
7	62	49	41	36	58	47	40	34	43	37	32	39	34	30	35	31	28
8	58	45	37	32	54	43	36	31	39	33	29	36	31	27	32	28	25
9	54	41	34	28	51	39	32	28	36	30	26	33	28	24	30	26	23
10	50	38	30	26	48	36	29	25	33	27	23	30	25	22	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17575	17575	17575	17575
5°	17587	20250	17637	15114
10°	17475	24505	17493	13197
15°	17233	29061	17374	11880
20°	17026	33460	17061	10932
25°	16716	34302	16754	10436
30°	16496	28340	16496	10112
35°	16223	18954	16121	9826
40°	15896	13682	15699	9387
45°	15484	10838	15038	8842
50°	14485	9203	13970	8306
55°	13388	8088	12843	7710
60°	12275	7043	11621	7082
65°	11052	6029	10518	6247
70°	9786	5005	9132	5266
75°	8365	3774	7825	4066
80°	6612	2520	6097	2670
85°	4563	1157	3650	1053

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 28344 cd/sqm

TEST NUMBER: P1011390

CATALOG NUMBER: S123DIP-B1165D585UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.6	2.3
10°-20°	515.8	7.3
20°-30°	867.8	12.3
30°-40°	980.7	13.9
40°-50°	878.4	12.4
50°-60°	709.1	10.0
60°-70°	494.1	7.0
70°-80°	259.3	3.7
80°-90°	63.7	0.9
90°-100°	153.8	2.2
100°-110°	450.4	6.4
110°-120°	439.8	6.2
120°-130°	350.3	5.0
130°-140°	276.4	3.9
140°-150°	206.2	2.9
150°-160°	143.7	2.0
160°-170°	84.4	1.2
170°-180°	27.5	0.4
0°-30°	1544.2	21.9
0°-40°	2524.9	35.8
0°-60°	4112.4	58.2
0°-90°	4929.6	69.8
90°-120°	1044.0	14.8
90°-150°	1876.8	26.6
90°-180°	2132.0	30.2
0°-180°	7062.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1633	1633	1633	1633	1633	
5°	1631	1940	1636	1448	1631	155
15°	1557	2887	1570	1180	1557	440
25°	1424	3427	1427	1043	1424	657
35°	1256	1846	1248	957	1256	786
45°	1043	997	1013	813	1043	797
55°	739	677	709	646	739	662
65°	457	440	435	456	457	455
75°	220	226	206	244	220	236
85°	48	52	38	48	48	55
90°	1	17	1	17	1	5
95°	20	67	20	67	20	21
105°	67	730	67	730	67	71
115°	118	888	118	888	118	116
125°	164	700	164	700	164	145
135°	192	568	192	568	192	148
145°	219	444	219	444	219	137
155°	248	368	248	368	248	114
165°	271	321	271	321	271	77
175°	283	289	283	289	283	27
180°	284	284	284	284	284	

TEST NUMBER: P1011390

CATALOG NUMBER: S123DIP-B1165D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8
2.5°	1637.5	1650.2	1656.5	1666.0	1675.5	1689.7	1694.5	1702.4	1699.2	1705.6	1708.7
5°	1631.2	1653.4	1672.3	1696.1	1718.2	1734.0	1749.9	1775.2	1794.2	1797.3	1811.6
7.5°	1620.1	1651.8	1685.0	1718.2	1760.9	1786.3	1814.7	1849.5	1878.0	1923.9	1941.3
10°	1605.9	1650.2	1697.7	1743.5	1802.1	1841.6	1876.4	1935.0	1993.5	2041.0	2085.3
12.5°	1583.7	1639.1	1700.8	1768.8	1844.8	1890.7	1938.1	2015.7	2104.3	2177.0	2224.5
15°	1556.8	1626.5	1705.6	1778.3	1862.2	1947.6	1998.3	2085.3	2211.9	2279.9	2401.7
17.5°	1534.7	1605.9	1685.0	1798.9	1912.8	1998.3	2034.6	2194.4	2281.5	2395.4	2533.0
20°	1499.9	1590.1	1691.3	1805.2	1952.4	2004.6	2078.9	2240.3	2347.9	2496.6	2665.9
22.5°	1463.5	1560.0	1681.8	1800.5	1965.0	2020.4	2121.7	2249.8	2420.7	2567.8	2754.5
25°	1423.9	1528.4	1651.8	1792.6	1954.0	2034.6	2129.6	2287.8	2472.9	2658.0	2830.5
27.5°	1384.4	1498.3	1626.5	1767.3	1923.9	2018.8	2113.8	2278.3	2515.6	2716.6	2936.5
30°	1346.4	1460.3	1588.5	1732.5	1897.0	1988.8	2078.9	2284.6	2548.8	2775.1	2996.6
32.5°	1305.3	1422.4	1556.8	1677.1	1843.2	1941.3	2042.6	2284.6	2569.4	2809.9	3012.4
35°	1256.2	1376.5	1492.0	1612.2	1776.8	1885.9	1999.8	2268.8	2588.4	2821.0	2946.0
37.5°	1208.8	1314.8	1414.4	1531.5	1704.0	1821.1	1952.4	2249.8	2578.9	2773.5	2808.3
40°	1155.0	1261.0	1341.7	1450.8	1632.8	1768.8	1901.7	2224.5	2537.8	2661.2	2559.9
42.5°	1102.8	1186.6	1256.2	1362.2	1560.0	1692.9	1836.9	2178.6	2457.1	2482.4	2254.6
45°	1042.6	1102.8	1164.5	1284.7	1480.9	1617.0	1776.8	2112.2	2327.3	2254.6	1966.6
47.5°	965.1	1018.9	1086.9	1197.7	1397.0	1537.9	1689.7	2026.7	2139.1	1987.2	1672.3
50°	890.8	936.6	999.9	1107.5	1308.4	1446.1	1607.5	1892.3	1947.6	1708.7	1441.3
52.5°	816.4	851.2	912.9	1020.5	1221.4	1354.3	1501.5	1754.6	1723.0	1466.7	1229.3
55°	738.9	768.9	827.5	933.5	1120.2	1246.7	1387.5	1585.3	1503.0	1259.4	1069.5
57.5°	662.9	694.6	754.7	843.3	1018.9	1142.3	1254.6	1409.7	1286.3	1091.7	924.0
60°	594.9	621.8	667.7	754.7	914.5	1014.2	1117.0	1223.0	1120.2	931.9	803.7
62.5°	523.7	549.0	591.7	670.8	808.5	897.1	979.4	1066.4	952.5	814.8	700.9
65°	457.2	477.8	517.4	590.1	702.5	775.3	841.7	901.8	810.1	683.5	598.1
67.5°	397.1	414.5	447.7	512.6	607.5	659.8	713.6	764.2	686.7	585.4	512.6
70°	332.3	346.5	376.6	424.0	500.0	553.8	593.3	631.3	561.7	481.0	431.9
72.5°	275.3	289.5	308.5	357.6	409.8	443.0	485.7	506.3	466.7	400.3	351.2
75°	219.9	231.0	248.4	280.0	329.1	351.2	378.1	394.0	357.6	313.3	283.2
77.5°	172.5	177.2	189.9	212.0	245.2	270.5	291.1	300.6	275.3	246.8	221.5
80°	121.8	128.2	137.6	156.6	181.9	189.9	202.5	213.6	197.8	172.5	156.6
82.5°	80.7	88.6	93.3	101.3	117.1	126.6	129.7	139.2	125.0	115.5	109.2
85°	47.5	50.6	52.2	57.0	64.9	69.6	74.4	75.9	72.8	71.2	64.9
87.5°	23.7	23.7	23.7	26.9	28.5	31.6	33.2	33.2	33.2	31.6	30.1
90°	1.1	2.3	3.4	5.2	6.3	6.9	7.5	9.2	10.9	12.6	14.3
92.5°	8.6	12.6	18.4	23.5	29.3	34.4	39.6	58.0	88.4	118.2	106.7
95°	19.5	21.2	27.5	37.3	52.2	63.4	74.6	123.4	208.9	303.0	340.3
97.5°	31.0	31.6	36.7	45.3	60.3	72.6	84.9	133.1	232.4	390.8	523.4
100°	42.5	43.0	47.1	55.1	68.9	80.1	91.2	131.4	216.3	367.3	543.4
102.5°	54.5	55.7	59.1	66.6	78.6	88.6	98.7	133.7	202.6	332.8	506.1
105°	66.6	68.3	71.7	78.6	89.5	98.4	107.3	138.3	197.4	305.9	461.4
107.5°	79.2	80.9	84.4	91.2	101.6	109.9	118.2	145.8	196.3	286.4	421.8
110°	93.0	94.7	97.6	103.9	113.6	121.6	129.7	155.5	199.1	276.0	389.1

TEST NUMBER: P1011390

CATALOG NUMBER: S123DIP-B1165D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	105.6	107.3	110.2	116.5	126.3	134.0	141.7	165.3	204.9	270.3	367.3
115°	117.6	119.9	123.4	129.1	138.9	146.6	154.4	176.2	211.2	269.7	352.9
117.5°	129.7	132.6	135.4	140.6	151.5	158.6	165.8	187.7	219.2	270.3	343.2
120°	142.3	144.0	146.9	152.6	163.6	170.8	177.9	198.6	228.4	272.6	336.9
122.5°	153.2	154.9	157.8	164.1	174.5	182.2	189.9	210.0	237.0	276.6	332.8
125°	163.6	164.7	168.1	174.5	185.4	193.2	200.9	220.9	246.2	280.6	329.4
127.5°	171.6	173.3	177.3	183.6	195.7	203.4	211.2	230.7	253.6	285.2	327.7
130°	179.0	180.8	185.9	192.8	204.9	212.6	220.4	239.3	261.1	289.8	326.0
132.5°	184.8	187.1	192.8	201.4	213.5	221.0	228.4	246.8	268.0	293.2	325.4
135°	191.7	194.0	200.3	208.9	220.9	228.6	236.4	254.2	273.7	296.7	324.8
137.5°	198.0	200.3	206.6	215.8	227.8	235.0	242.2	259.4	278.3	299.0	323.7
140°	204.3	207.2	212.9	222.1	233.6	240.8	247.9	264.6	281.8	301.3	323.1
142.5°	211.2	213.5	219.8	227.8	239.3	245.9	252.5	268.6	285.2	303.0	321.9
145°	218.6	220.4	225.5	234.1	243.9	250.5	257.1	272.0	287.5	303.6	320.8
147.5°	226.1	227.3	232.4	239.9	249.6	255.4	261.1	274.9	289.2	303.6	319.1
150°	233.6	234.1	238.7	246.2	254.2	259.4	264.6	277.8	289.8	303.6	316.8
152.5°	241.0	241.0	245.6	251.9	258.8	263.7	268.6	279.5	290.9	301.9	313.9
155°	248.5	248.5	251.9	257.7	264.0	268.0	272.0	281.8	290.9	300.7	310.5
157.5°	254.2	254.8	257.7	262.8	268.6	271.8	274.9	282.9	291.5	299.0	307.6
160°	261.1	261.1	263.4	268.0	272.0	274.9	277.8	284.6	291.5	297.8	304.1
162.5°	266.3	266.3	268.0	271.4	274.9	277.2	279.5	285.2	290.9	295.5	300.7
165°	271.4	270.9	272.0	274.9	277.2	279.2	281.2	285.8	289.8	293.2	297.3
167.5°	275.5	274.9	275.5	277.8	279.5	280.9	282.3	285.8	289.2	290.9	293.8
170°	278.9	277.8	278.3	280.0	281.2	281.8	282.3	285.2	287.5	288.7	290.4
172.5°	281.2	280.6	280.6	281.8	282.3	282.6	282.9	285.2	286.9	286.9	287.5
175°	282.9	282.3	281.8	282.9	282.9	283.2	283.5	284.6	285.8	285.2	285.2
177.5°	284.1	283.5	282.9	283.5	283.5	283.5	283.5	284.1	285.2	284.1	283.5
180°	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5

TEST NUMBER: P1011390

CATALOG NUMBER: S123DIP-B1165D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8
2.5°	1719.8	1723.0	1734.0	1742.0	1757.8	1756.2	1756.2	1754.6	1749.9	1757.8	1762.5
5°	1840.0	1866.9	1870.1	1904.9	1906.5	1920.7	1930.2	1922.3	1941.3	1939.7	1925.5
7.5°	1988.8	2025.2	2042.6	2075.8	2113.8	2104.3	2140.7	2147.0	2143.8	2159.6	2170.7
10°	2151.7	2215.0	2259.3	2321.0	2336.8	2346.3	2370.1	2390.6	2431.8	2400.1	2420.7
12.5°	2338.4	2384.3	2442.8	2540.9	2590.0	2621.6	2632.7	2646.9	2675.4	2658.0	2659.6
15°	2495.1	2556.8	2656.4	2778.3	2792.5	2832.1	2822.6	2908.0	2949.1	2887.4	2922.2
17.5°	2658.0	2740.3	2859.0	2965.0	3025.1	3052.0	3077.3	3159.6	3156.4	3146.9	3154.8
20°	2762.4	2896.9	3044.1	3184.9	3202.3	3222.8	3290.9	3325.7	3319.4	3346.3	3363.7
22.5°	2909.6	3052.0	3208.6	3302.0	3341.5	3365.2	3419.0	3441.2	3450.7	3457.0	3445.9
25°	3033.0	3184.9	3300.4	3382.6	3406.4	3419.0	3436.4	3442.8	3438.0	3426.9	3436.4
27.5°	3116.8	3238.7	3317.8	3355.7	3343.1	3322.5	3289.3	3267.1	3218.1	3194.4	3222.8
30°	3151.7	3205.4	3229.2	3165.9	3102.6	3052.0	2988.7	2871.6	2779.8	2806.7	2770.4
32.5°	3096.3	3061.5	2947.6	2784.6	2735.5	2653.3	2474.5	2336.8	2341.6	2268.8	2298.9
35°	2933.3	2775.1	2559.9	2313.1	2248.2	2203.9	2007.8	1977.7	1914.4	1846.4	1865.4
37.5°	2645.4	2414.4	2153.3	1971.4	1874.9	1778.3	1667.6	1601.1	1563.2	1534.7	1556.8
40°	2294.1	2012.5	1797.3	1634.4	1552.1	1490.4	1414.4	1348.0	1305.3	1300.5	1308.4
42.5°	1949.2	1711.9	1514.1	1359.1	1332.2	1259.4	1210.3	1158.1	1145.5	1124.9	1136.0
45°	1650.2	1457.2	1294.2	1167.6	1136.0	1117.0	1056.9	1023.7	1009.4	996.8	1015.7
47.5°	1433.4	1230.9	1112.3	1036.3	1004.7	973.0	939.8	917.6	906.6	908.2	906.6
50°	1224.6	1075.9	971.4	912.9	893.9	871.8	844.9	830.6	825.9	811.6	822.7
52.5°	1053.7	946.1	873.3	818.0	803.7	787.9	765.8	757.9	746.8	743.6	743.6
55°	916.1	832.2	773.7	737.3	719.9	707.2	694.6	685.1	677.2	677.2	677.2
57.5°	808.5	735.7	693.0	661.3	655.0	642.4	628.1	628.1	617.0	615.5	620.2
60°	716.7	651.8	618.6	591.7	582.2	579.1	564.8	564.8	561.7	553.8	560.1
62.5°	623.4	575.9	547.4	526.9	517.4	517.4	506.3	498.4	498.4	500.0	496.8
65°	537.9	503.1	477.8	462.0	457.2	450.9	449.3	443.0	438.3	439.8	438.3
67.5°	462.0	435.1	417.7	405.0	397.1	394.0	389.2	389.2	386.0	387.6	379.7
70°	394.0	367.1	352.8	340.2	337.0	337.0	330.7	332.3	329.1	333.8	330.7
72.5°	324.3	303.8	292.7	288.0	284.8	283.2	280.0	276.9	275.3	278.5	276.9
75°	262.6	245.2	237.3	234.2	231.0	231.0	229.4	227.8	226.2	226.2	226.2
77.5°	204.1	193.0	183.5	186.7	181.9	183.5	178.8	178.8	180.4	178.8	178.8
80°	150.3	142.4	142.4	139.2	132.9	136.1	136.1	131.3	129.7	132.9	128.2
82.5°	99.7	98.1	94.9	93.3	90.2	91.8	90.2	88.6	87.0	90.2	87.0
85°	58.5	58.5	57.0	53.8	57.0	55.4	53.8	53.8	52.2	52.2	52.2
87.5°	30.1	26.9	26.9	25.3	26.9	23.7	25.3	23.7	22.2	23.7	22.2
90°	13.8	14.3	14.9	15.5	16.0	16.6	16.1	16.6	17.2	16.6	17.2
92.5°	79.8	56.8	44.2	38.4	36.4	34.4	33.3	31.0	31.6	30.4	31.6
95°	276.0	206.6	140.0	109.6	99.2	88.9	78.0	72.9	68.9	66.6	68.9
97.5°	541.2	474.6	358.1	282.3	249.6	216.9	178.5	156.7	142.9	136.6	142.9
100°	656.5	676.6	630.1	563.0	522.2	481.5	423.5	381.6	359.2	359.8	359.2
102.5°	662.2	743.7	753.5	721.3	699.2	677.2	635.3	604.3	586.5	569.8	586.5
105°	626.1	746.0	803.4	814.3	806.8	799.4	773.0	751.2	732.8	730.0	732.8
107.5°	574.4	711.6	801.7	846.4	854.2	861.9	858.5	848.2	840.7	834.4	840.7
110°	526.2	657.6	763.2	835.5	855.6	875.7	891.8	896.4	895.2	894.1	895.2

TEST NUMBER: P1011390

CATALOG NUMBER: S123DIP-B1165D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	484.3	604.3	712.7	795.9	823.2	850.5	883.2	899.8	905.6	906.1	905.6
115°	452.2	558.4	658.2	742.6	773.8	805.1	848.2	873.4	884.9	887.8	884.9
117.5°	431.0	522.8	611.2	688.6	721.0	753.5	798.2	826.4	843.6	847.6	843.6
120°	414.9	495.8	573.3	642.2	671.2	700.1	745.4	777.6	791.4	794.8	791.4
122.5°	401.7	474.6	542.9	605.4	631.8	658.2	697.2	725.4	740.9	745.4	740.9
125°	390.8	456.2	518.8	573.9	596.8	619.8	656.5	681.8	696.1	700.1	696.1
127.5°	380.5	439.6	496.4	546.9	568.2	589.4	622.6	644.4	657.6	661.1	657.6
130°	372.4	424.1	475.7	522.2	541.7	561.2	591.7	612.3	624.4	629.0	624.4
132.5°	365.0	409.7	456.2	498.7	517.0	535.4	563.5	584.2	594.5	597.4	594.5
135°	358.7	397.1	437.9	475.2	491.6	507.9	536.0	553.2	563.5	567.6	563.5
137.5°	352.9	385.1	419.5	452.8	467.4	482.0	506.1	523.9	532.5	536.0	532.5
140°	347.8	374.7	404.0	431.5	443.8	456.2	478.0	494.1	503.3	502.7	503.3
142.5°	343.2	365.0	389.1	412.0	422.4	432.7	450.5	464.3	472.3	471.7	472.3
145°	339.2	357.5	376.5	394.8	403.2	411.5	425.8	437.9	442.4	443.6	442.4
147.5°	335.1	351.2	366.7	382.2	388.2	394.2	405.7	414.3	418.9	419.5	418.9
150°	331.1	344.3	357.5	369.6	375.0	380.5	389.1	395.4	398.8	398.8	398.8
152.5°	326.5	338.0	348.9	359.2	363.5	367.8	374.2	379.9	381.6	381.6	381.6
155°	321.9	331.7	340.9	349.5	353.0	356.4	361.5	366.1	367.3	367.8	367.3
157.5°	316.8	324.8	332.8	339.7	342.6	345.5	350.1	353.5	354.6	354.6	354.6
160°	311.6	319.1	325.4	331.1	333.1	335.1	339.2	342.6	342.6	342.0	342.6
162.5°	306.4	312.2	317.3	322.5	324.2	326.0	328.3	331.1	331.1	330.5	331.1
165°	301.9	306.4	309.9	313.9	315.4	316.8	319.1	321.4	320.8	320.8	320.8
167.5°	297.3	301.3	304.1	306.4	307.5	308.7	309.9	311.6	311.0	311.0	311.0
170°	293.2	296.1	297.8	300.1	300.7	301.3	301.9	303.0	302.4	302.4	302.4
172.5°	289.2	291.5	292.7	294.4	294.7	295.0	295.0	296.1	295.0	294.4	295.0
175°	286.4	287.5	288.1	289.2	289.2	289.2	289.2	289.8	289.2	288.7	289.2
177.5°	284.1	284.6	285.2	285.8	285.8	285.8	285.2	285.8	284.6	284.6	284.6
180°	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5

TEST NUMBER: P1011390

CATALOG NUMBER: S123DIP-B1165D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8
2.5°	1749.9	1754.6	1742.0	1738.8	1738.8	1745.1	1740.4	1697.7	1705.6	1696.1	1692.9
5°	1942.9	1933.4	1920.7	1914.4	1906.5	1884.3	1882.8	1833.7	1824.2	1792.6	1778.3
7.5°	2154.9	2147.0	2109.0	2104.3	2101.1	2080.5	2028.3	1976.1	1938.1	1901.7	1866.9
10°	2397.0	2373.2	2355.8	2321.0	2303.6	2275.1	2207.1	2158.1	2093.2	2037.8	1965.0
12.5°	2688.1	2661.2	2602.6	2577.3	2555.2	2476.1	2408.0	2352.7	2226.1	2188.1	2097.9
15°	2901.7	2844.7	2838.4	2783.0	2779.8	2692.8	2563.1	2503.0	2404.9	2265.6	2172.3
17.5°	3132.7	3082.0	3042.5	2976.0	2966.5	2884.3	2789.3	2642.2	2534.6	2401.7	2283.0
20°	3302.0	3275.1	3207.0	3180.1	3124.8	3055.1	2957.0	2775.1	2643.8	2510.9	2365.3
22.5°	3436.4	3409.5	3355.7	3319.4	3287.7	3197.5	3080.5	2925.4	2745.0	2571.0	2420.7
25°	3434.9	3426.9	3404.8	3387.4	3363.7	3297.2	3199.1	3050.4	2849.5	2658.0	2449.2
27.5°	3240.3	3262.4	3300.4	3319.4	3314.6	3305.1	3249.7	3124.8	2944.4	2716.6	2482.4
30°	2835.2	2915.9	2987.1	3082.0	3110.5	3180.1	3211.8	3140.6	2996.6	2784.6	2525.1
32.5°	2351.1	2468.2	2623.2	2675.4	2765.6	2900.1	3050.4	3077.3	2987.1	2824.1	2552.0
35°	1928.6	2025.2	2145.4	2227.7	2308.4	2526.7	2716.6	2881.1	2911.2	2803.6	2545.7
37.5°	1596.4	1664.4	1770.4	1840.0	1914.4	2101.1	2366.9	2580.5	2730.8	2734.0	2528.3
40°	1355.9	1386.0	1477.7	1528.4	1599.6	1760.9	1998.3	2276.7	2496.6	2597.9	2482.4
42.5°	1148.6	1188.2	1264.1	1302.1	1348.0	1488.8	1645.4	1909.7	2181.8	2398.5	2397.0
45°	1025.2	1053.7	1088.5	1120.2	1172.4	1256.2	1435.0	1632.8	1893.8	2139.1	2235.6
47.5°	916.1	943.0	977.8	987.3	1022.1	1101.2	1210.3	1382.8	1626.5	1870.1	2052.1
50°	824.3	846.5	870.2	887.6	903.4	968.3	1050.6	1196.1	1390.7	1626.5	1852.7
52.5°	753.1	768.9	789.5	799.0	813.2	860.7	924.0	1031.6	1191.4	1406.5	1626.5
55°	686.7	697.7	710.4	726.2	732.5	767.3	816.4	908.2	1026.8	1219.8	1428.7
57.5°	625.0	629.7	637.6	647.1	655.0	685.1	727.8	789.5	893.9	1042.6	1240.4
60°	555.3	568.0	572.7	582.2	587.0	610.7	643.9	696.1	776.8	905.0	1053.7
62.5°	496.8	504.7	512.6	517.4	528.4	536.4	563.2	610.7	677.2	772.1	906.6
65°	444.6	447.7	452.5	457.2	460.4	469.9	495.2	526.9	577.5	661.3	765.8
67.5°	384.5	387.6	394.0	395.5	398.7	411.4	425.6	452.5	495.2	558.5	643.9
70°	325.9	330.7	333.8	337.0	341.7	346.5	362.3	384.5	417.7	462.0	528.4
72.5°	275.3	280.0	280.0	283.2	281.6	288.0	303.8	319.6	341.7	378.1	436.7
75°	224.7	224.7	227.8	229.4	231.0	237.3	243.7	256.3	273.7	302.2	338.6
77.5°	177.2	175.6	178.8	178.8	178.8	183.5	189.9	196.2	207.3	227.8	256.3
80°	129.7	129.7	132.9	134.5	131.3	132.9	136.1	142.4	150.3	164.5	180.4
82.5°	85.4	91.8	90.2	91.8	90.2	93.3	94.9	96.5	99.7	106.0	117.1
85°	52.2	52.2	52.2	53.8	52.2	53.8	53.8	53.8	55.4	58.5	63.3
87.5°	22.2	22.2	22.2	23.7	22.2	22.2	23.7	22.2	23.7	23.7	25.3
90°	16.6	16.1	16.6	16.0	15.5	14.9	14.3	13.8	14.3	12.6	10.9
92.5°	31.0	33.3	34.4	36.4	38.4	44.2	56.8	79.8	106.7	118.2	88.4
95°	72.9	78.0	88.9	99.2	109.6	140.0	206.6	276.0	340.3	303.0	208.9
97.5°	156.7	178.5	216.9	249.6	282.3	358.1	474.6	541.2	523.4	390.8	232.4
100°	381.6	423.5	481.5	522.2	563.0	630.1	676.6	656.5	543.4	367.3	216.3
102.5°	604.3	635.3	677.2	699.2	721.3	753.5	743.7	662.2	506.1	332.8	202.6
105°	751.2	773.0	799.4	806.8	814.3	803.4	746.0	626.1	461.4	305.9	197.4
107.5°	848.2	858.5	861.9	854.2	846.4	801.7	711.6	574.4	421.8	286.4	196.3
110°	896.4	891.8	875.7	855.6	835.5	763.2	657.6	526.2	389.1	276.0	199.1

TEST NUMBER: P1011390

CATALOG NUMBER: S123DIP-B1165D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	899.8	883.2	850.5	823.2	795.9	712.7	604.3	484.3	367.3	270.3	204.9
115°	873.4	848.2	805.1	773.8	742.6	658.2	558.4	452.2	352.9	269.7	211.2
117.5°	826.4	798.2	753.5	721.0	688.6	611.2	522.8	431.0	343.2	270.3	219.2
120°	777.6	745.4	700.1	671.2	642.2	573.3	495.8	414.9	336.9	272.6	228.4
122.5°	725.4	697.2	658.2	631.8	605.4	542.9	474.6	401.7	332.8	276.6	237.0
125°	681.8	656.5	619.8	596.8	573.9	518.8	456.2	390.8	329.4	280.6	246.2
127.5°	644.4	622.6	589.4	568.2	546.9	496.4	439.6	380.5	327.7	285.2	253.6
130°	612.3	591.7	561.2	541.7	522.2	475.7	424.1	372.4	326.0	289.8	261.1
132.5°	584.2	563.5	535.4	517.0	498.7	456.2	409.7	365.0	325.4	293.2	268.0
135°	553.2	536.0	507.9	491.6	475.2	437.9	397.1	358.7	324.8	296.7	273.7
137.5°	523.9	506.1	482.0	467.4	452.8	419.5	385.1	352.9	323.7	299.0	278.3
140°	494.1	478.0	456.2	443.8	431.5	404.0	374.7	347.8	323.1	301.3	281.8
142.5°	464.3	450.5	432.7	422.4	412.0	389.1	365.0	343.2	321.9	303.0	285.2
145°	437.9	425.8	411.5	403.2	394.8	376.5	357.5	339.2	320.8	303.6	287.5
147.5°	414.3	405.7	394.2	388.2	382.2	366.7	351.2	335.1	319.1	303.6	289.2
150°	395.4	389.1	380.5	375.0	369.6	357.5	344.3	331.1	316.8	303.6	289.8
152.5°	379.9	374.2	367.8	363.5	359.2	348.9	338.0	326.5	313.9	301.9	290.9
155°	366.1	361.5	356.4	353.0	349.5	340.9	331.7	321.9	310.5	300.7	290.9
157.5°	353.5	350.1	345.5	342.6	339.7	332.8	324.8	316.8	307.6	299.0	291.5
160°	342.6	339.2	335.1	333.1	331.1	325.4	319.1	311.6	304.1	297.8	291.5
162.5°	331.1	328.3	326.0	324.2	322.5	317.3	312.2	306.4	300.7	295.5	290.9
165°	321.4	319.1	316.8	315.4	313.9	309.9	306.4	301.9	297.3	293.2	289.8
167.5°	311.6	309.9	308.7	307.5	306.4	304.1	301.3	297.3	293.8	290.9	289.2
170°	303.0	301.9	301.3	300.7	300.1	297.8	296.1	293.2	290.4	288.7	287.5
172.5°	296.1	295.0	295.0	294.7	294.4	292.7	291.5	289.2	287.5	286.9	286.9
175°	289.8	289.2	289.2	289.2	289.2	288.1	287.5	286.4	285.2	285.2	285.8
177.5°	285.8	285.2	285.8	285.8	285.8	285.2	284.6	284.1	283.5	284.1	285.2
180°	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5

TEST NUMBER: P1011390

CATALOG NUMBER: S123DIP-B1165D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8
2.5°	1677.1	1672.3	1672.3	1669.2	1659.7	1642.3	1640.7	1643.9	1634.4	1624.9	1610.6
5°	1759.4	1729.3	1719.8	1710.3	1691.3	1659.7	1647.0	1635.9	1618.5	1598.0	1575.8
7.5°	1829.0	1786.3	1773.6	1756.2	1718.2	1673.9	1645.4	1621.7	1598.0	1569.5	1542.6
10°	1916.0	1854.3	1824.2	1798.9	1746.7	1685.0	1642.3	1607.5	1569.5	1534.7	1499.9
12.5°	2014.1	1914.4	1904.9	1843.2	1783.1	1691.3	1639.1	1588.5	1537.9	1495.1	1458.7
15°	2096.4	1987.2	1947.6	1906.5	1791.0	1677.1	1626.5	1569.5	1511.0	1465.1	1411.3
17.5°	2148.6	2058.4	1974.5	1919.2	1798.9	1697.7	1599.6	1534.7	1473.0	1409.7	1365.4
20°	2211.9	2080.5	2007.8	1933.4	1814.7	1681.8	1583.7	1503.0	1427.1	1370.1	1316.4
22.5°	2275.1	2097.9	2037.8	1957.1	1817.9	1666.0	1555.3	1474.6	1387.5	1330.6	1272.1
25°	2268.8	2123.3	2023.6	1955.5	1786.3	1651.8	1522.0	1427.1	1346.4	1273.6	1215.1
27.5°	2273.6	2094.8	1993.5	1914.4	1764.1	1631.2	1487.2	1387.5	1303.7	1227.8	1166.0
30°	2275.1	2052.1	1963.5	1868.5	1723.0	1582.2	1447.7	1346.4	1257.8	1175.5	1120.2
32.5°	2270.4	2017.2	1906.5	1821.1	1658.1	1534.7	1401.8	1294.2	1204.0	1128.1	1075.9
35°	2259.3	1976.1	1848.0	1740.4	1591.6	1466.7	1359.1	1248.3	1151.8	1082.2	1022.1
37.5°	2229.3	1931.8	1786.3	1680.2	1514.1	1387.5	1292.6	1200.9	1107.5	1025.2	974.6
40°	2207.1	1871.7	1724.5	1609.1	1430.3	1306.9	1227.8	1140.7	1049.0	974.6	925.6
42.5°	2156.5	1814.7	1661.3	1523.6	1348.0	1221.4	1147.1	1077.4	998.3	925.6	881.3
45°	2074.2	1753.0	1583.7	1444.5	1257.8	1137.6	1069.5	1012.6	943.0	873.3	829.0
47.5°	1958.7	1664.4	1501.5	1362.2	1169.2	1047.4	979.4	936.6	881.3	822.7	784.7
50°	1833.7	1567.9	1417.6	1280.0	1083.8	965.1	898.7	859.1	822.7	768.9	732.5
52.5°	1670.8	1465.1	1321.1	1189.8	992.0	878.1	819.6	791.1	753.1	715.1	683.5
55°	1512.5	1332.2	1213.5	1088.5	901.8	795.8	738.9	708.8	686.7	655.0	629.7
57.5°	1329.0	1208.8	1099.6	985.7	818.0	721.5	667.7	631.3	617.0	602.8	579.1
60°	1159.7	1068.0	979.4	884.4	731.0	643.9	591.7	563.2	549.0	539.5	523.7
62.5°	1004.7	933.5	857.5	781.6	642.4	563.2	523.7	495.2	482.6	481.0	466.7
65°	855.9	805.3	743.6	669.3	560.1	490.5	452.5	435.1	420.9	420.9	409.8
67.5°	707.2	672.4	623.4	571.2	485.7	420.9	386.0	370.2	362.3	362.3	354.4
70°	588.6	564.8	520.5	474.6	400.3	351.2	324.3	310.1	305.4	306.9	300.6
72.5°	477.8	452.5	416.1	382.9	327.5	291.1	272.1	256.3	248.4	250.0	248.4
75°	370.2	357.6	325.9	300.6	256.3	231.0	213.6	205.7	199.4	200.9	197.8
77.5°	278.5	259.5	242.1	224.7	197.8	177.2	163.0	155.1	150.3	150.3	150.3
80°	189.9	186.7	172.5	163.0	140.8	125.0	113.9	112.3	107.6	107.6	107.6
82.5°	123.4	115.5	107.6	101.3	88.6	79.1	74.4	71.2	69.6	68.0	71.2
85°	68.0	63.3	60.1	53.8	49.0	44.3	39.6	38.0	36.4	38.0	36.4
87.5°	26.9	22.2	22.2	20.6	19.0	17.4	17.4	14.2	14.2	12.7	12.7
90°	9.2	7.5	6.9	6.3	5.2	3.4	2.3	1.1	2.3	3.4	5.2
92.5°	58.0	39.6	34.4	29.3	23.5	18.4	12.6	8.6	12.6	18.4	23.5
95°	123.4	74.6	63.4	52.2	37.3	27.5	21.2	19.5	21.2	27.5	37.3
97.5°	133.1	84.9	72.6	60.3	45.3	36.7	31.6	31.0	31.6	36.7	45.3
100°	131.4	91.2	80.1	68.9	55.1	47.1	43.0	42.5	43.0	47.1	55.1
102.5°	133.7	98.7	88.6	78.6	66.6	59.1	55.7	54.5	55.7	59.1	66.6
105°	138.3	107.3	98.4	89.5	78.6	71.7	68.3	66.6	68.3	71.7	78.6
107.5°	145.8	118.2	109.9	101.6	91.2	84.4	80.9	79.2	80.9	84.4	91.2
110°	155.5	129.7	121.6	113.6	103.9	97.6	94.7	93.0	94.7	97.6	103.9

TEST NUMBER: P1011390

CATALOG NUMBER: S123DIP-B1165D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	165.3	141.7	134.0	126.3	116.5	110.2	107.3	105.6	107.3	110.2	116.5
115°	176.2	154.4	146.6	138.9	129.1	123.4	119.9	117.6	119.9	123.4	129.1
117.5°	187.7	165.8	158.6	151.5	140.6	135.4	132.6	129.7	132.6	135.4	140.6
120°	198.6	177.9	170.8	163.6	152.6	146.9	144.0	142.3	144.0	146.9	152.6
122.5°	210.0	189.9	182.2	174.5	164.1	157.8	154.9	153.2	154.9	157.8	164.1
125°	220.9	200.9	193.2	185.4	174.5	168.1	164.7	163.6	164.7	168.1	174.5
127.5°	230.7	211.2	203.4	195.7	183.6	177.3	173.3	171.6	173.3	177.3	183.6
130°	239.3	220.4	212.6	204.9	192.8	185.9	180.8	179.0	180.8	185.9	192.8
132.5°	246.8	228.4	221.0	213.5	201.4	192.8	187.1	184.8	187.1	192.8	201.4
135°	254.2	236.4	228.6	220.9	208.9	200.3	194.0	191.7	194.0	200.3	208.9
137.5°	259.4	242.2	235.0	227.8	215.8	206.6	200.3	198.0	200.3	206.6	215.8
140°	264.6	247.9	240.8	233.6	222.1	212.9	207.2	204.3	207.2	212.9	222.1
142.5°	268.6	252.5	245.9	239.3	227.8	219.8	213.5	211.2	213.5	219.8	227.8
145°	272.0	257.1	250.5	243.9	234.1	225.5	220.4	218.6	220.4	225.5	234.1
147.5°	274.9	261.1	255.4	249.6	239.9	232.4	227.3	226.1	227.3	232.4	239.9
150°	277.8	264.6	259.4	254.2	246.2	238.7	234.1	233.6	234.1	238.7	246.2
152.5°	279.5	268.6	263.7	258.8	251.9	245.6	241.0	241.0	241.0	245.6	251.9
155°	281.8	272.0	268.0	264.0	257.7	251.9	248.5	248.5	248.5	251.9	257.7
157.5°	282.9	274.9	271.8	268.6	262.8	257.7	254.8	254.2	254.8	257.7	262.8
160°	284.6	277.8	274.9	272.0	268.0	263.4	261.1	261.1	261.1	263.4	268.0
162.5°	285.2	279.5	277.2	274.9	271.4	268.0	266.3	266.3	266.3	268.0	271.4
165°	285.8	281.2	279.2	277.2	274.9	272.0	270.9	271.4	270.9	272.0	274.9
167.5°	285.8	282.3	280.9	279.5	277.8	275.5	274.9	275.5	274.9	275.5	277.8
170°	285.2	282.3	281.8	281.2	280.0	278.3	277.8	278.9	277.8	278.3	280.0
172.5°	285.2	282.9	282.6	282.3	281.8	280.6	280.6	281.2	280.6	280.6	281.8
175°	284.6	283.5	283.2	282.9	282.9	281.8	282.3	282.9	282.3	281.8	282.9
177.5°	284.1	283.5	283.5	283.5	283.5	282.9	283.5	284.1	283.5	282.9	283.5
180°	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5

TEST NUMBER: P1011390

CATALOG NUMBER: S123DIP-B1165D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8
2.5°	1607.5	1605.9	1609.1	1599.6	1583.7	1575.8	1553.7	1548.9	1547.3	1548.9	1550.5
5°	1563.2	1561.6	1556.8	1541.0	1522.0	1507.8	1480.9	1479.3	1469.8	1460.3	1465.1
7.5°	1520.4	1514.1	1504.6	1484.1	1458.7	1442.9	1420.8	1405.0	1392.3	1384.4	1378.1
10°	1477.7	1468.2	1458.7	1431.8	1400.2	1376.5	1349.6	1336.9	1322.7	1316.4	1310.0
12.5°	1422.4	1412.9	1395.5	1363.8	1344.8	1314.8	1287.9	1275.2	1267.3	1254.6	1246.7
15°	1378.1	1359.1	1349.6	1316.4	1276.8	1273.6	1224.6	1221.4	1205.6	1205.6	1192.9
17.5°	1327.4	1313.2	1295.8	1262.6	1234.1	1205.6	1180.3	1170.8	1156.6	1153.4	1147.1
20°	1278.4	1259.4	1253.1	1219.8	1189.8	1155.0	1128.1	1118.6	1112.3	1105.9	1110.7
22.5°	1227.8	1211.9	1196.1	1166.0	1143.9	1109.1	1093.3	1083.8	1074.3	1071.1	1072.7
25°	1178.7	1164.5	1148.6	1118.6	1094.9	1066.4	1052.1	1047.4	1042.6	1042.6	1041.1
27.5°	1131.2	1117.0	1102.8	1075.9	1052.1	1031.6	1020.5	1015.7	1011.0	1014.2	1017.3
30°	1082.2	1069.5	1056.9	1033.1	1014.2	995.2	988.8	985.7	984.1	992.0	992.0
32.5°	1037.9	1026.8	1017.3	995.2	976.2	960.4	955.6	957.2	958.8	963.5	966.7
35°	992.0	984.1	974.6	955.6	939.8	925.6	927.1	927.1	930.3	938.2	944.5
37.5°	950.9	939.8	931.9	916.1	903.4	890.8	895.5	900.2	903.4	912.9	916.1
40°	901.8	897.1	890.8	874.9	863.9	862.3	863.9	867.0	873.3	878.1	882.8
42.5°	862.3	855.9	848.0	835.4	825.9	827.5	829.0	832.2	835.4	843.3	848.0
45°	818.0	813.2	806.9	795.8	787.9	789.5	791.1	791.1	794.2	803.7	806.9
47.5°	768.9	770.5	762.6	751.5	746.8	746.8	746.8	749.9	757.9	761.0	762.6
50°	721.5	718.3	716.7	705.6	702.5	700.9	702.5	704.1	715.1	713.6	718.3
52.5°	670.8	670.8	669.3	662.9	658.2	658.2	655.0	662.9	666.1	669.3	674.0
55°	621.8	617.0	615.5	612.3	606.0	604.4	607.5	617.0	620.2	623.4	628.1
57.5°	568.0	568.0	564.8	560.1	560.1	560.1	560.1	566.4	571.2	574.3	583.8
60°	518.9	512.6	507.9	507.9	507.9	506.3	515.8	515.8	525.3	526.9	530.0
62.5°	460.4	457.2	454.1	455.7	454.1	457.2	460.4	466.7	468.3	473.1	477.8
65°	405.0	405.0	401.9	411.4	405.0	405.0	412.9	412.9	416.1	420.9	427.2
67.5°	351.2	352.8	349.7	349.7	352.8	354.4	356.0	362.3	363.9	370.2	378.1
70°	295.9	299.0	300.6	297.4	300.6	303.8	306.9	308.5	314.8	318.0	322.8
72.5°	246.8	250.0	245.2	246.8	248.4	251.6	253.1	256.3	259.5	269.0	272.1
75°	197.8	196.2	194.6	200.9	197.8	204.1	205.7	205.7	208.8	216.8	219.9
77.5°	151.9	151.9	153.5	150.3	155.1	153.5	155.1	159.8	164.5	164.5	177.2
80°	106.0	109.2	109.2	109.2	110.8	112.3	109.2	117.1	118.7	118.7	123.4
82.5°	68.0	69.6	68.0	71.2	71.2	74.4	72.8	74.4	77.5	80.7	82.3
85°	36.4	36.4	39.6	39.6	38.0	39.6	38.0	39.6	42.7	42.7	44.3
87.5°	12.7	12.7	12.7	12.7	14.2	12.7	14.2	14.2	12.7	12.7	17.4
90°	6.3	6.9	7.5	9.2	10.9	12.6	14.3	13.8	14.3	14.9	15.5
92.5°	29.3	34.4	39.6	58.0	88.4	118.2	106.7	79.8	56.8	44.2	38.4
95°	52.2	63.4	74.6	123.4	208.9	303.0	340.3	276.0	206.6	140.0	109.6
97.5°	60.3	72.6	84.9	133.1	232.4	390.8	523.4	541.2	474.6	358.1	282.3
100°	68.9	80.1	91.2	131.4	216.3	367.3	543.4	656.5	676.6	630.1	563.0
102.5°	78.6	88.6	98.7	133.7	202.6	332.8	506.1	662.2	743.7	753.5	721.3
105°	89.5	98.4	107.3	138.3	197.4	305.9	461.4	626.1	746.0	803.4	814.3
107.5°	101.6	109.9	118.2	145.8	196.3	286.4	421.8	574.4	711.6	801.7	846.4
110°	113.6	121.6	129.7	155.5	199.1	276.0	389.1	526.2	657.6	763.2	835.5

TEST NUMBER: P1011390

CATALOG NUMBER: S123DIP-B1165D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	126.3	134.0	141.7	165.3	204.9	270.3	367.3	484.3	604.3	712.7	795.9
115°	138.9	146.6	154.4	176.2	211.2	269.7	352.9	452.2	558.4	658.2	742.6
117.5°	151.5	158.6	165.8	187.7	219.2	270.3	343.2	431.0	522.8	611.2	688.6
120°	163.6	170.8	177.9	198.6	228.4	272.6	336.9	414.9	495.8	573.3	642.2
122.5°	174.5	182.2	189.9	210.0	237.0	276.6	332.8	401.7	474.6	542.9	605.4
125°	185.4	193.2	200.9	220.9	246.2	280.6	329.4	390.8	456.2	518.8	573.9
127.5°	195.7	203.4	211.2	230.7	253.6	285.2	327.7	380.5	439.6	496.4	546.9
130°	204.9	212.6	220.4	239.3	261.1	289.8	326.0	372.4	424.1	475.7	522.2
132.5°	213.5	221.0	228.4	246.8	268.0	293.2	325.4	365.0	409.7	456.2	498.7
135°	220.9	228.6	236.4	254.2	273.7	296.7	324.8	358.7	397.1	437.9	475.2
137.5°	227.8	235.0	242.2	259.4	278.3	299.0	323.7	352.9	385.1	419.5	452.8
140°	233.6	240.8	247.9	264.6	281.8	301.3	323.1	347.8	374.7	404.0	431.5
142.5°	239.3	245.9	252.5	268.6	285.2	303.0	321.9	343.2	365.0	389.1	412.0
145°	243.9	250.5	257.1	272.0	287.5	303.6	320.8	339.2	357.5	376.5	394.8
147.5°	249.6	255.4	261.1	274.9	289.2	303.6	319.1	335.1	351.2	366.7	382.2
150°	254.2	259.4	264.6	277.8	289.8	303.6	316.8	331.1	344.3	357.5	369.6
152.5°	258.8	263.7	268.6	279.5	290.9	301.9	313.9	326.5	338.0	348.9	359.2
155°	264.0	268.0	272.0	281.8	290.9	300.7	310.5	321.9	331.7	340.9	349.5
157.5°	268.6	271.8	274.9	282.9	291.5	299.0	307.6	316.8	324.8	332.8	339.7
160°	272.0	274.9	277.8	284.6	291.5	297.8	304.1	311.6	319.1	325.4	331.1
162.5°	274.9	277.2	279.5	285.2	290.9	295.5	300.7	306.4	312.2	317.3	322.5
165°	277.2	279.2	281.2	285.8	289.8	293.2	297.3	301.9	306.4	309.9	313.9
167.5°	279.5	280.9	282.3	285.8	289.2	290.9	293.8	297.3	301.3	304.1	306.4
170°	281.2	281.8	282.3	285.2	287.5	288.7	290.4	293.2	296.1	297.8	300.1
172.5°	282.3	282.6	282.9	285.2	286.9	286.9	287.5	289.2	291.5	292.7	294.4
175°	282.9	283.2	283.5	284.6	285.8	285.2	285.2	286.4	287.5	288.1	289.2
177.5°	283.5	283.5	283.5	284.1	285.2	284.1	283.5	284.1	284.6	285.2	285.8
180°	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5

TEST NUMBER: P1011390

CATALOG NUMBER: S123DIP-B1165D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8
2.5°	1548.9	1550.5	1544.2	1539.4	1552.1	1544.2	1544.2	1545.8	1542.6	1547.3	1545.8
5°	1461.9	1463.5	1452.4	1455.6	1449.3	1447.7	1446.1	1455.6	1454.0	1452.4	1455.6
7.5°	1376.5	1376.5	1371.7	1368.6	1368.6	1363.8	1370.1	1368.6	1371.7	1371.7	1376.5
10°	1305.3	1308.4	1300.5	1292.6	1291.0	1292.6	1292.6	1294.2	1295.8	1306.9	1305.3
12.5°	1246.7	1242.0	1240.4	1235.7	1227.8	1224.6	1221.4	1238.8	1234.1	1234.1	1234.1
15°	1181.9	1192.9	1191.4	1177.1	1174.0	1180.3	1177.1	1177.1	1192.9	1191.4	1189.8
17.5°	1147.1	1143.9	1140.7	1132.8	1134.4	1132.8	1134.4	1134.4	1143.9	1143.9	1143.9
20°	1107.5	1101.2	1101.2	1098.0	1098.0	1093.3	1099.6	1101.2	1107.5	1107.5	1109.1
22.5°	1072.7	1068.0	1068.0	1066.4	1069.5	1063.2	1069.5	1071.1	1071.1	1075.9	1075.9
25°	1042.6	1039.5	1039.5	1042.6	1042.6	1042.6	1042.6	1049.0	1044.2	1045.8	1044.2
27.5°	1015.7	1017.3	1018.9	1020.5	1018.9	1020.5	1022.1	1025.2	1026.8	1025.2	1022.1
30°	990.4	995.2	996.8	996.8	999.9	1001.5	1003.1	1003.1	1004.7	999.9	1003.1
32.5°	971.4	971.4	974.6	976.2	979.4	980.9	980.9	984.1	982.5	977.8	979.4
35°	944.5	944.5	950.9	954.0	958.8	957.2	958.8	958.8	960.4	957.2	952.5
37.5°	917.6	920.8	920.8	927.1	928.7	930.3	928.7	931.9	930.3	927.1	925.6
40°	886.0	884.4	886.0	890.8	892.3	892.3	892.3	895.5	895.5	895.5	893.9
42.5°	846.5	851.2	849.6	854.4	852.8	852.8	855.9	859.1	860.7	855.9	857.5
45°	808.5	808.5	811.6	811.6	813.2	813.2	819.6	816.4	819.6	816.4	818.0
47.5°	767.3	768.9	768.9	770.5	773.7	776.8	773.7	775.3	775.3	776.8	773.7
50°	721.5	721.5	724.6	729.4	735.7	732.5	731.0	737.3	732.5	732.5	729.4
52.5°	674.0	678.7	680.3	685.1	689.8	691.4	693.0	689.8	691.4	686.7	688.2
55°	628.1	629.7	636.0	640.8	645.5	645.5	643.9	645.5	647.1	640.8	640.8
57.5°	582.2	587.0	593.3	593.3	599.6	599.6	598.1	598.1	599.6	594.9	593.3
60°	533.2	537.9	545.8	545.8	555.3	556.9	553.8	550.6	550.6	545.8	547.4
62.5°	481.0	485.7	490.5	498.4	504.7	501.5	507.9	501.5	503.1	493.6	493.6
65°	435.1	436.7	444.6	452.5	452.5	455.7	452.5	454.1	449.3	449.3	443.0
67.5°	381.3	381.3	389.2	397.1	405.0	405.0	405.0	400.3	400.3	395.5	395.5
70°	333.8	332.3	340.2	344.9	349.7	351.2	348.1	346.5	343.3	338.6	337.0
72.5°	275.3	278.5	286.4	289.5	297.4	295.9	303.8	294.3	294.3	286.4	284.8
75°	223.1	226.2	234.2	238.9	243.7	243.7	248.4	243.7	237.3	234.2	232.6
77.5°	177.2	175.6	181.9	189.9	191.4	189.9	193.0	191.4	185.1	185.1	181.9
80°	126.6	131.3	137.6	136.1	142.4	140.8	140.8	137.6	137.6	132.9	136.1
82.5°	83.9	88.6	90.2	88.6	90.2	93.3	94.9	93.3	93.3	90.2	91.8
85°	44.3	44.3	47.5	49.0	47.5	47.5	49.0	53.8	50.6	47.5	50.6
87.5°	14.2	12.7	12.7	14.2	12.7	12.7	14.2	14.2	15.8	15.8	15.8
90°	16.0	16.6	16.1	16.6	17.2	16.6	17.2	16.6	16.1	16.6	16.0
92.5°	36.4	34.4	33.3	31.0	31.6	30.4	31.6	31.0	33.3	34.4	36.4
95°	99.2	88.9	78.0	72.9	68.9	66.6	68.9	72.9	78.0	88.9	99.2
97.5°	249.6	216.9	178.5	156.7	142.9	136.6	142.9	156.7	178.5	216.9	249.6
100°	522.2	481.5	423.5	381.6	359.2	359.8	359.2	381.6	423.5	481.5	522.2
102.5°	699.2	677.2	635.3	604.3	586.5	569.8	586.5	604.3	635.3	677.2	699.2
105°	806.8	799.4	773.0	751.2	732.8	730.0	732.8	751.2	773.0	799.4	806.8
107.5°	854.2	861.9	858.5	848.2	840.7	834.4	840.7	848.2	858.5	861.9	854.2
110°	855.6	875.7	891.8	896.4	895.2	894.1	895.2	896.4	891.8	875.7	855.6



TEST NUMBER: P1011390

CATALOG NUMBER: S123DIP-B1165D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	823.2	850.5	883.2	899.8	905.6	906.1	905.6	899.8	883.2	850.5	823.2
115°	773.8	805.1	848.2	873.4	884.9	887.8	884.9	873.4	848.2	805.1	773.8
117.5°	721.0	753.5	798.2	826.4	843.6	847.6	843.6	826.4	798.2	753.5	721.0
120°	671.2	700.1	745.4	777.6	791.4	794.8	791.4	777.6	745.4	700.1	671.2
122.5°	631.8	658.2	697.2	725.4	740.9	745.4	740.9	725.4	697.2	658.2	631.8
125°	596.8	619.8	656.5	681.8	696.1	700.1	696.1	681.8	656.5	619.8	596.8
127.5°	568.2	589.4	622.6	644.4	657.6	661.1	657.6	644.4	622.6	589.4	568.2
130°	541.7	561.2	591.7	612.3	624.4	629.0	624.4	612.3	591.7	561.2	541.7
132.5°	517.0	535.4	563.5	584.2	594.5	597.4	594.5	584.2	563.5	535.4	517.0
135°	491.6	507.9	536.0	553.2	563.5	567.6	563.5	553.2	536.0	507.9	491.6
137.5°	467.4	482.0	506.1	523.9	532.5	536.0	532.5	523.9	506.1	482.0	467.4
140°	443.8	456.2	478.0	494.1	503.3	502.7	503.3	494.1	478.0	456.2	443.8
142.5°	422.4	432.7	450.5	464.3	472.3	471.7	472.3	464.3	450.5	432.7	422.4
145°	403.2	411.5	425.8	437.9	442.4	443.6	442.4	437.9	425.8	411.5	403.2
147.5°	388.2	394.2	405.7	414.3	418.9	419.5	418.9	414.3	405.7	394.2	388.2
150°	375.0	380.5	389.1	395.4	398.8	398.8	398.8	395.4	389.1	380.5	375.0
152.5°	363.5	367.8	374.2	379.9	381.6	381.6	381.6	379.9	374.2	367.8	363.5
155°	353.0	356.4	361.5	366.1	367.3	367.8	367.3	366.1	361.5	356.4	353.0
157.5°	342.6	345.5	350.1	353.5	354.6	354.6	354.6	353.5	350.1	345.5	342.6
160°	333.1	335.1	339.2	342.6	342.6	342.0	342.6	342.6	339.2	335.1	333.1
162.5°	324.2	326.0	328.3	331.1	331.1	330.5	331.1	331.1	328.3	326.0	324.2
165°	315.4	316.8	319.1	321.4	320.8	320.8	320.8	321.4	319.1	316.8	315.4
167.5°	307.5	308.7	309.9	311.6	311.0	311.0	311.0	311.6	309.9	308.7	307.5
170°	300.7	301.3	301.9	303.0	302.4	302.4	302.4	303.0	301.9	301.3	300.7
172.5°	294.7	295.0	295.0	296.1	295.0	294.4	295.0	296.1	295.0	295.0	294.7
175°	289.2	289.2	289.2	289.8	289.2	288.7	289.2	289.8	289.2	289.2	289.2
177.5°	285.8	285.8	285.2	285.8	284.6	284.6	284.6	285.8	285.2	285.8	285.8
180°	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5

TEST NUMBER: P1011390

CATALOG NUMBER: S123DIP-B1165D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8
2.5°	1550.5	1553.7	1555.3	1548.9	1544.2	1552.1	1563.2	1571.1	1577.4	1585.3	1590.1
5°	1458.7	1469.8	1469.8	1473.0	1477.7	1485.6	1506.2	1520.4	1533.1	1542.6	1550.5
7.5°	1381.2	1389.1	1393.9	1401.8	1409.7	1420.8	1444.5	1465.1	1484.1	1495.1	1507.8
10°	1311.6	1317.9	1325.8	1330.6	1344.8	1360.7	1390.7	1408.1	1430.3	1447.7	1463.5
12.5°	1245.2	1267.3	1272.1	1270.5	1283.1	1300.5	1330.6	1357.5	1381.2	1398.6	1416.0
15°	1197.7	1205.6	1215.1	1213.5	1240.4	1245.2	1270.5	1302.1	1333.8	1344.8	1360.7
17.5°	1145.5	1158.1	1167.6	1172.4	1180.3	1197.7	1221.4	1245.2	1286.3	1287.9	1329.0
20°	1104.3	1117.0	1123.3	1129.7	1134.4	1155.0	1175.5	1202.4	1235.7	1253.1	1275.2
22.5°	1077.4	1083.8	1088.5	1093.3	1099.6	1110.7	1136.0	1166.0	1188.2	1207.2	1221.4
25°	1045.8	1052.1	1058.5	1061.6	1066.4	1072.7	1091.7	1115.4	1147.1	1159.7	1174.0
27.5°	1023.7	1023.7	1026.8	1026.8	1033.1	1039.5	1053.7	1075.9	1101.2	1117.0	1136.0
30°	999.9	998.3	999.9	998.3	996.8	1006.2	1018.9	1037.9	1055.3	1074.3	1086.9
32.5°	976.2	974.6	974.6	976.2	969.9	974.6	980.9	998.3	1017.3	1026.8	1041.1
35°	950.9	947.7	947.7	947.7	944.5	941.4	947.7	963.5	976.2	988.8	999.9
37.5°	925.6	920.8	920.8	917.6	914.5	909.7	909.7	922.4	939.8	944.5	958.8
40°	890.8	890.8	887.6	886.0	882.8	879.7	874.9	886.0	901.8	906.6	917.6
42.5°	855.9	851.2	849.6	849.6	849.6	844.9	841.7	849.6	859.1	867.0	873.3
45°	816.4	813.2	814.8	813.2	810.1	808.5	806.9	810.1	821.1	824.3	832.2
47.5°	773.7	772.1	772.1	770.5	768.9	770.5	764.2	772.1	775.3	778.4	784.7
50°	729.4	727.8	726.2	724.6	724.6	726.2	724.6	724.6	731.0	734.1	740.4
52.5°	685.1	680.3	680.3	678.7	678.7	675.6	678.7	680.3	683.5	686.7	689.8
55°	637.6	637.6	632.9	632.9	629.7	629.7	631.3	629.7	636.0	639.2	639.2
57.5°	591.7	585.4	587.0	583.8	580.7	579.1	579.1	582.2	585.4	585.4	588.6
60°	542.7	536.4	534.8	528.4	531.6	526.9	528.4	528.4	534.8	531.6	534.8
62.5°	493.6	485.7	481.0	477.8	477.8	479.4	476.2	474.6	477.8	481.0	487.3
65°	441.4	436.7	431.9	427.2	427.2	425.6	428.8	424.0	422.4	424.0	427.2
67.5°	387.6	382.9	378.1	373.4	375.0	370.2	367.1	371.8	368.6	370.2	373.4
70°	335.4	332.3	322.8	319.6	318.0	319.6	318.0	314.8	319.6	318.0	319.6
72.5°	283.2	280.0	275.3	267.4	267.4	265.8	264.2	264.2	262.6	262.6	262.6
75°	232.6	226.2	221.5	219.9	216.8	215.2	213.6	210.4	212.0	213.6	210.4
77.5°	180.4	172.5	170.9	170.9	166.1	166.1	167.7	166.1	164.5	164.5	164.5
80°	132.9	126.6	126.6	123.4	120.2	120.2	120.2	120.2	118.7	117.1	118.7
82.5°	85.4	83.9	82.3	82.3	85.4	79.1	82.3	80.7	79.1	79.1	77.5
85°	47.5	49.0	47.5	49.0	45.9	47.5	47.5	47.5	45.9	47.5	44.3
87.5°	17.4	17.4	17.4	19.0	19.0	19.0	19.0	19.0	20.6	19.0	19.0
90°	15.5	14.9	14.3	13.8	14.3	12.6	10.9	9.2	7.5	6.9	6.3
92.5°	38.4	44.2	56.8	79.8	106.7	118.2	88.4	58.0	39.6	34.4	29.3
95°	109.6	140.0	206.6	276.0	340.3	303.0	208.9	123.4	74.6	63.4	52.2
97.5°	282.3	358.1	474.6	541.2	523.4	390.8	232.4	133.1	84.9	72.6	60.3
100°	563.0	630.1	676.6	656.5	543.4	367.3	216.3	131.4	91.2	80.1	68.9
102.5°	721.3	753.5	743.7	662.2	506.1	332.8	202.6	133.7	98.7	88.6	78.6
105°	814.3	803.4	746.0	626.1	461.4	305.9	197.4	138.3	107.3	98.4	89.5
107.5°	846.4	801.7	711.6	574.4	421.8	286.4	196.3	145.8	118.2	109.9	101.6
110°	835.5	763.2	657.6	526.2	389.1	276.0	199.1	155.5	129.7	121.6	113.6

TEST NUMBER: P1011390

CATALOG NUMBER: S123DIP-B1165D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	795.9	712.7	604.3	484.3	367.3	270.3	204.9	165.3	141.7	134.0	126.3
115°	742.6	658.2	558.4	452.2	352.9	269.7	211.2	176.2	154.4	146.6	138.9
117.5°	688.6	611.2	522.8	431.0	343.2	270.3	219.2	187.7	165.8	158.6	151.5
120°	642.2	573.3	495.8	414.9	336.9	272.6	228.4	198.6	177.9	170.8	163.6
122.5°	605.4	542.9	474.6	401.7	332.8	276.6	237.0	210.0	189.9	182.2	174.5
125°	573.9	518.8	456.2	390.8	329.4	280.6	246.2	220.9	200.9	193.2	185.4
127.5°	546.9	496.4	439.6	380.5	327.7	285.2	253.6	230.7	211.2	203.4	195.7
130°	522.2	475.7	424.1	372.4	326.0	289.8	261.1	239.3	220.4	212.6	204.9
132.5°	498.7	456.2	409.7	365.0	325.4	293.2	268.0	246.8	228.4	221.0	213.5
135°	475.2	437.9	397.1	358.7	324.8	296.7	273.7	254.2	236.4	228.6	220.9
137.5°	452.8	419.5	385.1	352.9	323.7	299.0	278.3	259.4	242.2	235.0	227.8
140°	431.5	404.0	374.7	347.8	323.1	301.3	281.8	264.6	247.9	240.8	233.6
142.5°	412.0	389.1	365.0	343.2	321.9	303.0	285.2	268.6	252.5	245.9	239.3
145°	394.8	376.5	357.5	339.2	320.8	303.6	287.5	272.0	257.1	250.5	243.9
147.5°	382.2	366.7	351.2	335.1	319.1	303.6	289.2	274.9	261.1	255.4	249.6
150°	369.6	357.5	344.3	331.1	316.8	303.6	289.8	277.8	264.6	259.4	254.2
152.5°	359.2	348.9	338.0	326.5	313.9	301.9	290.9	279.5	268.6	263.7	258.8
155°	349.5	340.9	331.7	321.9	310.5	300.7	290.9	281.8	272.0	268.0	264.0
157.5°	339.7	332.8	324.8	316.8	307.6	299.0	291.5	282.9	274.9	271.8	268.6
160°	331.1	325.4	319.1	311.6	304.1	297.8	291.5	284.6	277.8	274.9	272.0
162.5°	322.5	317.3	312.2	306.4	300.7	295.5	290.9	285.2	279.5	277.2	274.9
165°	313.9	309.9	306.4	301.9	297.3	293.2	289.8	285.8	281.2	279.2	277.2
167.5°	306.4	304.1	301.3	297.3	293.8	290.9	289.2	285.8	282.3	280.9	279.5
170°	300.1	297.8	296.1	293.2	290.4	288.7	287.5	285.2	282.3	281.8	281.2
172.5°	294.4	292.7	291.5	289.2	287.5	286.9	286.9	285.2	282.9	282.6	282.3
175°	289.2	288.1	287.5	286.4	285.2	285.2	285.8	284.6	283.5	283.2	282.9
177.5°	285.8	285.2	284.6	284.1	283.5	284.1	285.2	284.1	283.5	283.5	283.5
180°	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5

TEST NUMBER: P1011390

CATALOG NUMBER: S123DIP-B1165D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1632.8	1632.8	1632.8	1632.8
2.5°	1598.0	1602.7	1618.5	1637.5
5°	1566.3	1579.0	1601.1	1631.2
7.5°	1531.5	1550.5	1582.2	1620.1
10°	1492.0	1518.9	1558.4	1605.9
12.5°	1449.3	1484.1	1534.7	1583.7
15°	1422.4	1457.2	1503.0	1556.8
17.5°	1370.1	1411.3	1458.7	1534.7
20°	1316.4	1362.2	1423.9	1499.9
22.5°	1275.2	1324.3	1382.8	1463.5
25°	1226.2	1276.8	1340.1	1423.9
27.5°	1174.0	1224.6	1295.8	1384.4
30°	1134.4	1183.5	1251.5	1346.4
32.5°	1086.9	1134.4	1205.6	1305.3
35°	1033.1	1086.9	1155.0	1256.2
37.5°	992.0	1041.1	1112.3	1208.8
40°	947.7	990.4	1060.0	1155.0
42.5°	900.2	947.7	1007.8	1102.8
45°	855.9	890.8	952.5	1042.6
47.5°	808.5	848.0	895.5	965.1
50°	757.9	791.1	843.3	890.8
52.5°	708.8	735.7	780.0	816.4
55°	656.6	683.5	716.7	738.9
57.5°	607.5	626.5	648.7	662.9
60°	547.4	566.4	580.7	594.9
62.5°	493.6	507.9	515.8	523.7
65°	438.3	446.2	450.9	457.2
67.5°	378.1	386.0	387.6	397.1
70°	322.8	324.3	327.5	332.3
72.5°	270.5	273.7	272.1	275.3
75°	216.8	219.9	216.8	219.9
77.5°	164.5	167.7	167.7	172.5
80°	118.7	120.2	121.8	121.8
82.5°	77.5	82.3	79.1	80.7
85°	44.3	45.9	45.9	47.5
87.5°	20.6	22.2	20.6	23.7
90°	5.2	3.4	2.3	1.1
92.5°	23.5	18.4	12.6	8.6
95°	37.3	27.5	21.2	19.5
97.5°	45.3	36.7	31.6	31.0
100°	55.1	47.1	43.0	42.5
102.5°	66.6	59.1	55.7	54.5
105°	78.6	71.7	68.3	66.6
107.5°	91.2	84.4	80.9	79.2
110°	103.9	97.6	94.7	93.0

TEST NUMBER: P1011390

CATALOG NUMBER: S123DIP-B1165D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	116.5	110.2	107.3	105.6
115°	129.1	123.4	119.9	117.6
117.5°	140.6	135.4	132.6	129.7
120°	152.6	146.9	144.0	142.3
122.5°	164.1	157.8	154.9	153.2
125°	174.5	168.1	164.7	163.6
127.5°	183.6	177.3	173.3	171.6
130°	192.8	185.9	180.8	179.0
132.5°	201.4	192.8	187.1	184.8
135°	208.9	200.3	194.0	191.7
137.5°	215.8	206.6	200.3	198.0
140°	222.1	212.9	207.2	204.3
142.5°	227.8	219.8	213.5	211.2
145°	234.1	225.5	220.4	218.6
147.5°	239.9	232.4	227.3	226.1
150°	246.2	238.7	234.1	233.6
152.5°	251.9	245.6	241.0	241.0
155°	257.7	251.9	248.5	248.5
157.5°	262.8	257.7	254.8	254.2
160°	268.0	263.4	261.1	261.1
162.5°	271.4	268.0	266.3	266.3
165°	274.9	272.0	270.9	271.4
167.5°	277.8	275.5	274.9	275.5
170°	280.0	278.3	277.8	278.9
172.5°	281.8	280.6	280.6	281.2
175°	282.9	281.8	282.3	282.9
177.5°	283.5	282.9	283.5	284.1
180°	283.5	283.5	283.5	283.5

(END OF REPORT)