

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011408

Luminaire Tested: S123DIP-B1165D585UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011408
REPORT IS A COMBINATION OF REPORTS P989552 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1165D585UB50-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6762.0 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011408

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1011408

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74
1	103	98	94	91	97	93	90	87	83	81	79	75	73	71	66	65	64
2	94	86	80	75	88	82	76	72	74	69	66	66	63	60	59	56	54
3	86	76	69	63	81	72	66	60	65	60	56	59	54	51	52	49	46
4	79	68	60	54	74	64	57	52	58	52	48	52	48	44	47	43	40
5	72	61	52	46	68	58	50	45	52	46	41	47	42	38	43	38	35
6	67	55	46	40	63	52	44	39	47	41	36	43	38	34	39	34	31
7	62	49	41	36	58	47	40	34	43	37	32	39	34	30	35	31	28
8	58	45	37	32	54	43	36	31	39	33	29	36	31	27	32	28	25
9	54	41	34	28	51	39	32	28	36	30	26	33	28	24	30	26	23
10	50	38	30	26	48	36	29	25	33	27	23	30	25	22	28	24	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16826	16826	16826	16826
5°	16837	19388	16886	14469
10°	16731	23460	16747	12635
15°	16499	27823	16633	11373
20°	16301	32034	16335	10466
25°	16005	32841	16040	9992
30°	15793	27132	15793	9681
35°	15532	18146	15434	9407
40°	15219	13099	15030	8987
45°	14824	10376	14397	8466
50°	13868	8812	13375	7953
55°	12818	7743	12296	7381
60°	11751	6743	11126	6781
65°	10583	5773	10071	5980
70°	9368	4792	8743	5042
75°	8007	3614	7490	3892
80°	6330	2412	5836	2556
85°	4361	1108	3496	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 27137 cd/sqm

TEST NUMBER: P1011408

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.7	2.3
10°-20°	493.8	7.3
20°-30°	830.9	12.3
30°-40°	938.9	13.9
40°-50°	841.0	12.4
50°-60°	678.9	10.0
60°-70°	473.1	7.0
70°-80°	248.3	3.7
80°-90°	61.0	0.9
90°-100°	147.3	2.2
100°-110°	431.4	6.4
110°-120°	421.3	6.2
120°-130°	335.5	5.0
130°-140°	264.7	3.9
140°-150°	197.5	2.9
150°-160°	137.7	2.0
160°-170°	80.9	1.2
170°-180°	26.3	0.4
0°-30°	1478.4	21.9
0°-40°	2417.3	35.7
0°-60°	3937.1	58.2
0°-90°	4719.5	69.8
90°-120°	1000.0	14.8
90°-150°	1797.7	26.6
90°-180°	2043.0	30.2
0°-180°	6762.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1563	1563	1563	1563	1563	
5°	1562	1857	1566	1386	1562	148
15°	1490	2764	1503	1130	1490	421
25°	1363	3281	1366	998	1363	629
35°	1203	1768	1195	916	1203	753
45°	998	954	969	779	998	763
55°	707	648	679	618	707	633
65°	438	421	417	436	438	436
75°	210	217	197	233	210	226
85°	45	50	36	45	45	52
90°	1	16	1	16	1	5
95°	19	64	19	64	19	20
105°	64	699	64	699	64	68
115°	113	850	113	850	113	112
125°	157	671	157	671	157	139
135°	184	544	184	544	184	142
145°	209	425	209	425	209	131
155°	238	352	238	352	238	109
165°	260	307	260	307	260	73
175°	271	276	271	276	271	26
180°	272	272	272	272	272	

TEST NUMBER: P1011408

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1567.7	1579.9	1585.9	1595.0	1604.1	1617.7	1622.3	1629.9	1626.8	1632.9	1635.9
5°	1561.7	1582.9	1601.1	1623.8	1645.0	1660.1	1675.3	1699.5	1717.7	1720.7	1734.4
7.5°	1551.1	1581.4	1613.2	1645.0	1685.9	1710.1	1737.4	1770.7	1798.0	1841.9	1858.6
10°	1537.5	1579.9	1625.3	1669.2	1725.3	1763.1	1796.5	1852.5	1908.6	1954.0	1996.4
12.5°	1516.2	1569.3	1628.3	1693.5	1766.2	1810.1	1855.5	1929.8	2014.6	2084.3	2129.7
15°	1490.5	1557.1	1632.9	1702.6	1782.8	1864.6	1913.1	1996.4	2117.6	2182.7	2299.4
17.5°	1469.3	1537.5	1613.2	1722.3	1831.3	1913.1	1947.9	2100.9	2184.2	2293.3	2425.1
20°	1436.0	1522.3	1619.2	1728.3	1869.2	1919.2	1990.4	2144.9	2247.9	2390.2	2552.3
22.5°	1401.1	1493.5	1610.2	1723.8	1881.3	1934.3	2031.3	2153.9	2317.5	2458.4	2637.1
25°	1363.3	1463.2	1581.4	1716.2	1870.7	1947.9	2038.8	2190.3	2367.5	2544.8	2709.9
27.5°	1325.4	1434.5	1557.1	1692.0	1841.9	1932.8	2023.7	2181.2	2408.4	2600.8	2811.3
30°	1289.0	1398.1	1520.8	1658.6	1816.2	1904.0	1990.4	2187.3	2440.2	2656.8	2868.9
32.5°	1249.7	1361.7	1490.5	1605.6	1764.7	1858.6	1955.5	2187.3	2459.9	2690.2	2884.1
35°	1202.7	1317.8	1428.4	1543.5	1701.0	1805.6	1914.6	2172.1	2478.1	2700.8	2820.4
37.5°	1157.3	1258.7	1354.2	1466.3	1631.4	1743.5	1869.2	2153.9	2469.0	2655.3	2688.6
40°	1105.8	1207.2	1284.5	1389.0	1563.2	1693.5	1820.7	2129.7	2429.6	2547.8	2450.8
42.5°	1055.8	1136.0	1202.7	1304.2	1493.5	1620.8	1758.6	2085.8	2352.4	2376.6	2158.5
45°	998.2	1055.8	1114.8	1230.0	1417.8	1548.1	1701.0	2022.2	2228.2	2158.5	1882.8
47.5°	924.0	975.5	1040.6	1146.7	1337.5	1472.3	1617.7	1940.4	2047.9	1902.5	1601.1
50°	852.8	896.7	957.3	1060.3	1252.7	1384.5	1539.0	1811.6	1864.6	1635.9	1379.9
52.5°	781.6	814.9	874.0	977.0	1169.4	1296.6	1437.5	1679.8	1649.5	1404.2	1176.9
55°	707.4	736.2	792.2	893.7	1072.4	1193.6	1328.4	1517.8	1439.0	1205.7	1024.0
57.5°	634.7	665.0	722.5	807.4	975.5	1093.6	1201.2	1349.6	1231.5	1045.2	884.6
60°	569.5	595.3	639.2	722.5	875.5	970.9	1069.4	1170.9	1072.4	892.2	769.5
62.5°	501.4	525.6	566.5	642.2	774.0	858.9	937.6	1020.9	911.9	780.1	671.0
65°	437.8	457.4	495.3	565.0	672.5	742.2	805.8	863.4	775.5	654.4	572.6
67.5°	380.2	396.9	428.7	490.8	581.7	631.6	683.1	731.6	657.4	560.5	490.8
70°	318.1	331.7	360.5	405.9	478.7	530.2	568.0	604.4	537.7	460.5	413.5
72.5°	263.6	277.2	295.4	342.3	392.3	424.1	465.0	484.7	446.8	383.2	336.3
75°	210.5	221.2	237.8	268.1	315.1	336.3	362.0	377.2	342.3	299.9	271.1
77.5°	165.1	169.7	181.8	203.0	234.8	259.0	278.7	287.8	263.6	236.3	212.1
80°	116.6	122.7	131.8	150.0	174.2	181.8	193.9	204.5	189.3	165.1	150.0
82.5°	77.3	84.8	89.4	96.9	112.1	121.2	124.2	133.3	119.7	110.6	104.5
85°	45.4	48.5	50.0	54.5	62.1	66.6	71.2	72.7	69.7	68.2	62.1
87.5°	22.7	22.7	22.7	25.8	27.3	30.3	31.8	31.8	31.8	30.3	28.8
90°	1.1	2.2	3.3	4.9	6.0	6.6	7.1	8.8	10.4	12.1	13.7
92.5°	8.2	12.1	17.6	22.5	28.0	33.0	37.9	55.5	84.6	113.2	102.2
95°	18.7	20.3	26.4	35.7	50.0	60.8	71.5	118.2	200.1	290.2	325.9
97.5°	29.7	30.2	35.2	43.4	57.7	69.5	81.3	127.5	222.6	374.3	501.3
100°	40.7	41.2	45.1	52.8	66.0	76.7	87.4	125.9	207.2	351.8	520.5
102.5°	52.2	53.3	56.6	63.8	75.3	84.9	94.5	128.1	194.0	318.8	484.8
105°	63.8	65.4	68.7	75.3	85.7	94.2	102.8	132.5	189.1	293.0	441.9
107.5°	75.9	77.5	80.8	87.4	97.3	105.2	113.2	139.6	188.0	274.3	404.0
110°	89.0	90.7	93.4	99.5	108.8	116.5	124.2	149.0	190.7	264.4	372.7

TEST NUMBER: P1011408

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	101.1	102.8	105.5	111.6	120.9	128.4	135.8	158.3	196.2	258.9	351.8
115°	112.7	114.9	118.2	123.7	133.0	140.4	147.9	168.7	202.3	258.3	338.0
117.5°	124.2	127.0	129.7	134.7	145.1	152.0	158.9	179.7	210.0	258.9	328.7
120°	136.3	138.0	140.7	146.2	156.7	163.6	170.4	190.2	218.8	261.1	322.7
122.5°	146.8	148.4	151.2	157.2	167.1	174.5	181.9	201.2	227.0	264.9	318.8
125°	156.7	157.8	161.1	167.1	177.5	185.0	192.4	211.6	235.8	268.8	315.5
127.5°	164.3	166.0	169.8	175.9	187.4	194.9	202.3	221.0	243.0	273.2	313.9
130°	171.5	173.1	178.1	184.7	196.2	203.6	211.1	229.2	250.1	277.6	312.2
132.5°	177.0	179.2	184.7	192.9	204.5	211.6	218.8	236.4	256.7	280.9	311.7
135°	183.6	185.8	191.8	200.1	211.6	219.0	226.5	243.5	262.2	284.2	311.1
137.5°	189.6	191.8	197.9	206.7	218.2	225.1	232.0	248.4	266.6	286.4	310.0
140°	195.7	198.4	203.9	212.7	223.7	230.6	237.5	253.4	269.9	288.6	309.5
142.5°	202.3	204.5	210.5	218.2	229.2	235.6	241.9	257.2	273.2	290.2	308.4
145°	209.4	211.1	216.0	224.3	233.6	239.9	246.2	260.5	275.4	290.8	307.3
147.5°	216.6	217.7	222.6	229.8	239.1	244.6	250.1	263.3	277.0	290.8	305.6
150°	223.7	224.3	228.7	235.8	243.5	248.4	253.4	266.0	277.6	290.8	303.4
152.5°	230.9	230.9	235.3	241.3	247.9	252.6	257.2	267.7	278.7	289.1	300.7
155°	238.0	238.0	241.3	246.8	252.8	256.6	260.5	269.9	278.7	288.0	297.4
157.5°	243.5	244.0	246.8	251.7	257.2	260.2	263.3	271.0	279.2	286.4	294.6
160°	250.1	250.1	252.3	256.7	260.5	263.2	266.0	272.6	279.2	285.3	291.3
162.5°	255.0	255.0	256.7	260.0	263.3	265.5	267.7	273.2	278.7	283.1	288.0
165°	260.0	259.4	260.5	263.3	265.5	267.4	269.3	273.7	277.6	280.9	284.7
167.5°	263.8	263.3	263.8	266.0	267.7	269.0	270.4	273.7	277.0	278.7	281.4
170°	267.1	266.0	266.6	268.2	269.3	269.8	270.4	273.2	275.4	276.5	278.1
172.5°	269.3	268.8	268.8	269.9	270.4	270.7	271.0	273.2	274.8	274.8	275.4
175°	271.0	270.4	269.9	271.0	271.0	271.2	271.5	272.6	273.7	273.2	273.2
177.5°	272.1	271.5	271.0	271.5	271.5	271.5	271.5	272.1	273.2	272.1	271.5
180°	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5

TEST NUMBER: P1011408

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1646.5	1649.5	1660.1	1667.7	1682.9	1681.4	1681.4	1679.8	1675.3	1682.9	1687.4
5°	1761.6	1787.4	1790.4	1823.7	1825.3	1838.9	1848.0	1840.4	1858.6	1857.1	1843.4
7.5°	1904.0	1938.9	1955.5	1987.3	2023.7	2014.6	2049.4	2055.5	2052.5	2067.6	2078.2
10°	2060.0	2120.6	2163.0	2222.1	2237.3	2246.3	2269.1	2288.8	2328.1	2297.8	2317.5
12.5°	2238.8	2282.7	2338.7	2432.7	2479.6	2509.9	2520.5	2534.1	2561.4	2544.8	2546.3
15°	2388.7	2447.8	2543.2	2659.9	2673.5	2711.4	2702.3	2784.1	2823.5	2764.4	2797.7
17.5°	2544.8	2623.5	2737.1	2838.6	2896.2	2921.9	2946.2	3024.9	3021.9	3012.8	3020.4
20°	2644.7	2773.5	2914.3	3049.2	3065.8	3085.5	3150.6	3184.0	3177.9	3203.7	3220.3
22.5°	2785.6	2921.9	3071.9	3161.2	3199.1	3221.8	3273.3	3294.5	3303.6	3309.7	3299.1
25°	2903.7	3049.2	3159.7	3238.5	3261.2	3273.3	3290.0	3296.1	3291.5	3280.9	3290.0
27.5°	2984.0	3100.7	3176.4	3212.7	3200.6	3180.9	3149.1	3127.9	3081.0	3058.2	3085.5
30°	3017.3	3068.8	3091.6	3031.0	2970.4	2921.9	2861.3	2749.2	2661.4	2687.1	2652.3
32.5°	2964.3	2931.0	2821.9	2665.9	2619.0	2540.2	2369.0	2237.3	2241.8	2172.1	2200.9
35°	2808.3	2656.8	2450.8	2214.5	2152.4	2110.0	1922.2	1893.4	1832.8	1767.7	1785.9
37.5°	2532.6	2311.5	2061.6	1887.4	1795.0	1702.6	1596.5	1532.9	1496.6	1469.3	1490.5
40°	2196.4	1926.7	1720.7	1564.7	1486.0	1426.9	1354.2	1290.6	1249.7	1245.1	1252.7
42.5°	1866.2	1638.9	1449.6	1301.2	1275.4	1205.7	1158.8	1108.8	1096.7	1077.0	1087.6
45°	1579.9	1395.1	1239.1	1117.9	1087.6	1069.4	1011.8	980.0	966.4	954.3	972.5
47.5°	1372.3	1178.5	1064.9	992.1	961.9	931.6	899.8	878.5	867.9	869.5	867.9
50°	1172.4	1030.0	930.0	874.0	855.8	834.6	808.9	795.2	790.7	777.1	787.7
52.5°	1008.8	905.8	836.1	783.1	769.5	754.3	733.1	725.6	715.0	711.9	711.9
55°	877.0	796.7	740.7	705.9	689.2	677.1	665.0	655.9	648.3	648.3	648.3
57.5°	774.0	704.4	663.5	633.2	627.1	615.0	601.3	601.3	590.7	589.2	593.8
60°	686.2	624.1	592.3	566.5	557.4	554.4	540.8	540.8	537.7	530.2	536.2
62.5°	596.8	551.4	524.1	504.4	495.3	495.3	484.7	477.1	477.1	478.7	475.6
65°	515.0	481.7	457.4	442.3	437.8	431.7	430.2	424.1	419.6	421.1	419.6
67.5°	442.3	416.6	399.9	387.8	380.2	377.2	372.6	372.6	369.6	371.1	363.5
70°	377.2	351.4	337.8	325.7	322.6	322.6	316.6	318.1	315.1	319.6	316.6
72.5°	310.5	290.8	280.2	275.7	272.7	271.1	268.1	265.1	263.6	266.6	265.1
75°	251.4	234.8	227.2	224.2	221.2	221.2	219.6	218.1	216.6	216.6	216.6
77.5°	195.4	184.8	175.7	178.7	174.2	175.7	171.2	171.2	172.7	171.2	171.2
80°	143.9	136.3	136.3	133.3	127.2	130.3	130.3	125.7	124.2	127.2	122.7
82.5°	95.4	93.9	90.9	89.4	86.3	87.9	86.3	84.8	83.3	86.3	83.3
85°	56.0	56.0	54.5	51.5	54.5	53.0	51.5	51.5	50.0	50.0	50.0
87.5°	28.8	25.8	25.8	24.2	25.8	22.7	24.2	22.7	21.2	22.7	21.2
90°	13.2	13.7	14.3	14.8	15.4	15.9	15.4	15.9	16.5	15.9	16.5
92.5°	76.4	54.4	42.3	36.8	34.9	33.0	31.9	29.7	30.2	29.1	30.2
95°	264.4	197.9	134.1	105.0	95.1	85.2	74.8	69.8	66.0	63.8	66.0
97.5°	518.3	454.6	343.0	270.4	239.1	207.8	170.9	150.1	136.9	130.8	136.9
100°	628.8	648.1	603.5	539.2	500.2	461.2	405.7	365.5	344.1	344.6	344.1
102.5°	634.3	712.4	721.7	690.9	669.8	648.6	608.5	578.8	561.8	545.8	561.8
105°	599.7	714.6	769.5	780.0	772.8	765.7	740.4	719.5	701.9	699.2	701.9
107.5°	550.2	681.6	767.9	810.8	818.2	825.6	822.3	812.4	805.3	799.2	805.3
110°	504.0	629.9	731.0	800.3	819.6	838.8	854.2	858.6	857.5	856.4	857.5

TEST NUMBER: P1011408

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	463.9	578.8	682.7	762.4	788.5	814.6	845.9	861.9	867.4	867.9	867.4
115°	433.1	534.8	630.5	711.3	741.2	771.2	812.4	836.6	847.6	850.3	847.6
117.5°	412.8	500.7	585.4	659.6	690.7	721.7	764.6	791.5	808.0	811.8	808.0
120°	397.4	474.9	549.1	615.1	642.8	670.6	714.0	744.8	758.0	761.3	758.0
122.5°	384.8	454.6	520.0	579.9	605.2	630.5	667.8	694.8	709.6	714.0	709.6
125°	374.3	437.0	496.9	549.7	571.7	593.6	628.8	653.0	666.7	670.6	666.7
127.5°	364.4	421.0	475.5	523.8	544.2	564.5	596.4	617.3	629.9	633.2	629.9
130°	356.7	406.2	455.7	500.2	518.9	537.6	566.7	586.5	598.0	602.4	598.0
132.5°	349.6	392.5	437.0	477.7	495.2	512.8	539.8	559.6	569.4	572.2	569.4
135°	343.5	380.4	419.4	455.1	470.8	486.5	513.4	529.9	539.8	543.6	539.8
137.5°	338.0	368.8	401.8	433.7	447.7	461.7	484.8	501.8	510.1	513.4	510.1
140°	333.1	358.9	387.0	413.3	425.2	437.0	457.9	473.3	482.1	481.5	482.1
142.5°	328.7	349.6	372.7	394.7	404.5	414.4	431.5	444.7	452.4	451.8	452.4
145°	324.8	342.4	360.6	378.2	386.2	394.1	407.8	419.4	423.8	424.9	423.8
147.5°	321.0	336.4	351.2	366.1	371.8	377.6	388.6	396.9	401.3	401.8	401.3
150°	317.2	329.8	342.4	354.0	359.2	364.4	372.7	378.7	382.0	382.0	382.0
152.5°	312.8	323.8	334.2	344.1	348.2	352.3	358.4	363.9	365.5	365.5	365.5
155°	308.4	317.7	326.5	334.7	338.0	341.3	346.3	350.7	351.8	352.3	351.8
157.5°	303.4	311.1	318.8	325.4	328.2	330.9	335.3	338.6	339.7	339.7	339.7
160°	298.5	305.6	311.7	317.2	319.1	321.0	324.8	328.1	328.1	327.6	328.1
162.5°	293.5	299.0	304.0	308.9	310.5	312.2	314.4	317.2	317.2	316.6	317.2
165°	289.1	293.5	296.8	300.7	302.0	303.4	305.6	307.8	307.3	307.3	307.3
167.5°	284.7	288.6	291.3	293.5	294.6	295.7	296.8	298.5	297.9	297.9	297.9
170°	280.9	283.6	285.3	287.5	288.0	288.6	289.1	290.2	289.7	289.7	289.7
172.5°	277.0	279.2	280.3	282.0	282.2	282.5	282.5	283.6	282.5	282.0	282.5
175°	274.3	275.4	275.9	277.0	277.0	277.0	277.0	277.6	277.0	276.5	277.0
177.5°	272.1	272.6	273.2	273.7	273.7	273.7	273.2	273.7	272.6	272.6	272.6
180°	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5

TEST NUMBER: P1011408

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1675.3	1679.8	1667.7	1664.7	1664.7	1670.7	1666.2	1625.3	1632.9	1623.8	1620.8
5°	1860.1	1851.0	1838.9	1832.8	1825.3	1804.0	1802.5	1755.6	1746.5	1716.2	1702.6
7.5°	2063.1	2055.5	2019.1	2014.6	2011.6	1991.9	1941.9	1891.9	1855.5	1820.7	1787.4
10°	2294.8	2272.1	2255.4	2222.1	2205.5	2178.2	2113.1	2066.1	2004.0	1951.0	1881.3
12.5°	2573.5	2547.8	2491.7	2467.5	2446.3	2370.6	2305.4	2252.4	2131.2	2094.9	2008.5
15°	2778.0	2723.5	2717.4	2664.4	2661.4	2578.1	2453.9	2396.3	2302.4	2169.1	2079.7
17.5°	2999.2	2950.7	2912.8	2849.2	2840.1	2761.4	2670.5	2529.6	2426.6	2299.4	2185.8
20°	3161.2	3135.5	3070.4	3044.6	2991.6	2924.9	2831.0	2656.8	2531.1	2403.9	2264.5
22.5°	3290.0	3264.2	3212.7	3177.9	3147.6	3061.3	2949.2	2800.7	2628.1	2461.4	2317.5
25°	3288.5	3280.9	3259.7	3243.0	3220.3	3156.7	3062.8	2920.4	2728.0	2544.8	2344.8
27.5°	3102.2	3123.4	3159.7	3177.9	3173.4	3164.3	3111.3	2991.6	2818.9	2600.8	2376.6
30°	2714.4	2791.7	2859.8	2950.7	2978.0	3044.6	3074.9	3006.7	2868.9	2665.9	2417.5
32.5°	2250.9	2363.0	2511.4	2561.4	2647.8	2776.5	2920.4	2946.2	2859.8	2703.8	2443.3
35°	1846.5	1938.9	2054.0	2132.7	2210.0	2419.0	2600.8	2758.3	2787.1	2684.1	2437.2
37.5°	1528.4	1593.5	1695.0	1761.6	1832.8	2011.6	2266.0	2470.5	2614.4	2617.5	2420.5
40°	1298.1	1326.9	1414.8	1463.2	1531.4	1685.9	1913.1	2179.7	2390.2	2487.2	2376.6
42.5°	1099.7	1137.6	1210.3	1246.6	1290.6	1425.4	1575.3	1828.3	2088.8	2296.3	2294.8
45°	981.5	1008.8	1042.1	1072.4	1122.4	1202.7	1373.9	1563.2	1813.1	2047.9	2140.3
47.5°	877.0	902.8	936.1	945.2	978.5	1054.3	1158.8	1323.9	1557.1	1790.4	1964.6
50°	789.2	810.4	833.1	849.8	864.9	927.0	1005.8	1145.1	1331.4	1557.1	1773.8
52.5°	721.0	736.2	755.9	764.9	778.6	824.0	884.6	987.6	1140.6	1346.6	1557.1
55°	657.4	668.0	680.1	695.3	701.3	734.6	781.6	869.5	983.1	1167.9	1367.8
57.5°	598.3	602.9	610.4	619.5	627.1	655.9	696.8	755.9	855.8	998.2	1187.6
60°	531.7	543.8	548.3	557.4	562.0	584.7	616.5	666.5	743.7	866.4	1008.8
62.5°	475.6	483.2	490.8	495.3	505.9	513.5	539.2	584.7	648.3	739.2	867.9
65°	425.6	428.7	433.2	437.8	440.8	449.9	474.1	504.4	552.9	633.2	733.1
67.5°	368.1	371.1	377.2	378.7	381.7	393.8	407.5	433.2	474.1	534.7	616.5
70°	312.0	316.6	319.6	322.6	327.2	331.7	346.9	368.1	399.9	442.3	505.9
72.5°	263.6	268.1	268.1	271.1	269.6	275.7	290.8	306.0	327.2	362.0	418.1
75°	215.1	215.1	218.1	219.6	221.2	227.2	233.3	245.4	262.0	289.3	324.2
77.5°	169.7	168.1	171.2	171.2	171.2	175.7	181.8	187.8	198.4	218.1	245.4
80°	124.2	124.2	127.2	128.8	125.7	127.2	130.3	136.3	143.9	157.5	172.7
82.5°	81.8	87.9	86.3	87.9	86.3	89.4	90.9	92.4	95.4	101.5	112.1
85°	50.0	50.0	50.0	51.5	50.0	51.5	51.5	51.5	53.0	56.0	60.6
87.5°	21.2	21.2	21.2	22.7	21.2	21.2	22.7	21.2	22.7	22.7	24.2
90°	15.9	15.4	15.9	15.4	14.8	14.3	13.7	13.2	13.7	12.1	10.4
92.5°	29.7	31.9	33.0	34.9	36.8	42.3	54.4	76.4	102.2	113.2	84.6
95°	69.8	74.8	85.2	95.1	105.0	134.1	197.9	264.4	325.9	290.2	200.1
97.5°	150.1	170.9	207.8	239.1	270.4	343.0	454.6	518.3	501.3	374.3	222.6
100°	365.5	405.7	461.2	500.2	539.2	603.5	648.1	628.8	520.5	351.8	207.2
102.5°	578.8	608.5	648.6	669.8	690.9	721.7	712.4	634.3	484.8	318.8	194.0
105°	719.5	740.4	765.7	772.8	780.0	769.5	714.6	599.7	441.9	293.0	189.1
107.5°	812.4	822.3	825.6	818.2	810.8	767.9	681.6	550.2	404.0	274.3	188.0
110°	858.6	854.2	838.8	819.6	800.3	731.0	629.9	504.0	372.7	264.4	190.7

TEST NUMBER: P1011408

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	861.9	845.9	814.6	788.5	762.4	682.7	578.8	463.9	351.8	258.9	196.2
115°	836.6	812.4	771.2	741.2	711.3	630.5	534.8	433.1	338.0	258.3	202.3
117.5°	791.5	764.6	721.7	690.7	659.6	585.4	500.7	412.8	328.7	258.9	210.0
120°	744.8	714.0	670.6	642.8	615.1	549.1	474.9	397.4	322.7	261.1	218.8
122.5°	694.8	667.8	630.5	605.2	579.9	520.0	454.6	384.8	318.8	264.9	227.0
125°	653.0	628.8	593.6	571.7	549.7	496.9	437.0	374.3	315.5	268.8	235.8
127.5°	617.3	596.4	564.5	544.2	523.8	475.5	421.0	364.4	313.9	273.2	243.0
130°	586.5	566.7	537.6	518.9	500.2	455.7	406.2	356.7	312.2	277.6	250.1
132.5°	559.6	539.8	512.8	495.2	477.7	437.0	392.5	349.6	311.7	280.9	256.7
135°	529.9	513.4	486.5	470.8	455.1	419.4	380.4	343.5	311.1	284.2	262.2
137.5°	501.8	484.8	461.7	447.7	433.7	401.8	368.8	338.0	310.0	286.4	266.6
140°	473.3	457.9	437.0	425.2	413.3	387.0	358.9	333.1	309.5	288.6	269.9
142.5°	444.7	431.5	414.4	404.5	394.7	372.7	349.6	328.7	308.4	290.2	273.2
145°	419.4	407.8	394.1	386.2	378.2	360.6	342.4	324.8	307.3	290.8	275.4
147.5°	396.9	388.6	377.6	371.8	366.1	351.2	336.4	321.0	305.6	290.8	277.0
150°	378.7	372.7	364.4	359.2	354.0	342.4	329.8	317.2	303.4	290.8	277.6
152.5°	363.9	358.4	352.3	348.2	344.1	334.2	323.8	312.8	300.7	289.1	278.7
155°	350.7	346.3	341.3	338.0	334.7	326.5	317.7	308.4	297.4	288.0	278.7
157.5°	338.6	335.3	330.9	328.2	325.4	318.8	311.1	303.4	294.6	286.4	279.2
160°	328.1	324.8	321.0	319.1	317.2	311.7	305.6	298.5	291.3	285.3	279.2
162.5°	317.2	314.4	312.2	310.5	308.9	304.0	299.0	293.5	288.0	283.1	278.7
165°	307.8	305.6	303.4	302.0	300.7	296.8	293.5	289.1	284.7	280.9	277.6
167.5°	298.5	296.8	295.7	294.6	293.5	291.3	288.6	284.7	281.4	278.7	277.0
170°	290.2	289.1	288.6	288.0	287.5	285.3	283.6	280.9	278.1	276.5	275.4
172.5°	283.6	282.5	282.5	282.2	282.0	280.3	279.2	277.0	275.4	274.8	274.8
175°	277.6	277.0	277.0	277.0	277.0	275.9	275.4	274.3	273.2	273.2	273.7
177.5°	273.7	273.2	273.7	273.7	273.7	273.2	272.6	272.1	271.5	272.1	273.2
180°	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5

TEST NUMBER: P1011408

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1605.6	1601.1	1601.1	1598.0	1589.0	1572.3	1570.8	1573.8	1564.7	1555.6	1542.0
5°	1684.4	1655.6	1646.5	1637.4	1619.2	1589.0	1576.8	1566.2	1549.6	1529.9	1508.7
7.5°	1751.0	1710.1	1698.0	1681.4	1645.0	1602.6	1575.3	1552.6	1529.9	1502.6	1476.9
10°	1834.3	1775.3	1746.5	1722.3	1672.3	1613.2	1572.3	1539.0	1502.6	1469.3	1436.0
12.5°	1928.3	1832.8	1823.7	1764.7	1707.1	1619.2	1569.3	1520.8	1472.3	1431.4	1396.6
15°	2007.0	1902.5	1864.6	1825.3	1714.7	1605.6	1557.1	1502.6	1446.6	1402.6	1351.1
17.5°	2057.0	1970.7	1890.4	1837.4	1722.3	1625.3	1531.4	1469.3	1410.2	1349.6	1307.2
20°	2117.6	1991.9	1922.2	1851.0	1737.4	1610.2	1516.2	1439.0	1366.3	1311.8	1260.3
22.5°	2178.2	2008.5	1951.0	1873.7	1740.4	1595.0	1489.0	1411.7	1328.4	1273.9	1217.8
25°	2172.1	2032.8	1937.3	1872.2	1710.1	1581.4	1457.2	1366.3	1289.0	1219.4	1163.3
27.5°	2176.7	2005.5	1908.6	1832.8	1688.9	1561.7	1423.8	1328.4	1248.1	1175.4	1116.4
30°	2178.2	1964.6	1879.8	1788.9	1649.5	1514.7	1386.0	1289.0	1204.2	1125.4	1072.4
32.5°	2173.6	1931.3	1825.3	1743.5	1587.4	1469.3	1342.1	1239.1	1152.7	1080.0	1030.0
35°	2163.0	1891.9	1769.2	1666.2	1523.8	1404.2	1301.2	1195.1	1102.7	1036.1	978.5
37.5°	2134.3	1849.5	1710.1	1608.6	1449.6	1328.4	1237.5	1149.7	1060.3	981.5	933.1
40°	2113.1	1791.9	1651.1	1540.5	1369.3	1251.2	1175.4	1092.1	1004.3	933.1	886.1
42.5°	2064.6	1737.4	1590.5	1458.7	1290.6	1169.4	1098.2	1031.5	955.8	886.1	843.7
45°	1985.8	1678.3	1516.2	1383.0	1204.2	1089.1	1024.0	969.4	902.8	836.1	793.7
47.5°	1875.2	1593.5	1437.5	1304.2	1119.4	1002.8	937.6	896.7	843.7	787.7	751.3
50°	1755.6	1501.1	1357.2	1225.4	1037.6	924.0	860.4	822.5	787.7	736.2	701.3
52.5°	1599.6	1402.6	1264.8	1139.1	949.7	840.7	784.6	757.4	721.0	684.7	654.4
55°	1448.1	1275.4	1161.8	1042.1	863.4	761.9	707.4	678.6	657.4	627.1	602.9
57.5°	1272.4	1157.3	1052.7	943.7	783.1	690.7	639.2	604.4	590.7	577.1	554.4
60°	1110.3	1022.4	937.6	846.7	699.8	616.5	566.5	539.2	525.6	516.5	501.4
62.5°	961.9	893.7	821.0	748.3	615.0	539.2	501.4	474.1	462.0	460.5	446.8
65°	819.5	771.0	711.9	640.7	536.2	469.6	433.2	416.6	402.9	402.9	392.3
67.5°	677.1	643.8	596.8	546.8	465.0	402.9	369.6	354.4	346.9	346.9	339.3
70°	563.5	540.8	498.3	454.4	383.2	336.3	310.5	296.9	292.3	293.9	287.8
72.5°	457.4	433.2	398.4	366.6	313.5	278.7	260.5	245.4	237.8	239.3	237.8
75°	354.4	342.3	312.0	287.8	245.4	221.2	204.5	196.9	190.9	192.4	189.3
77.5°	266.6	248.4	231.8	215.1	189.3	169.7	156.0	148.4	143.9	143.9	143.9
80°	181.8	178.7	165.1	156.0	134.8	119.7	109.1	107.5	103.0	103.0	103.0
82.5°	118.1	110.6	103.0	96.9	84.8	75.7	71.2	68.2	66.6	65.1	68.2
85°	65.1	60.6	57.6	51.5	47.0	42.4	37.9	36.4	34.8	36.4	34.8
87.5°	25.8	21.2	21.2	19.7	18.2	16.7	16.7	13.6	13.6	12.1	12.1
90°	8.8	7.1	6.6	6.0	4.9	3.3	2.2	1.1	2.2	3.3	4.9
92.5°	55.5	37.9	33.0	28.0	22.5	17.6	12.1	8.2	12.1	17.6	22.5
95°	118.2	71.5	60.8	50.0	35.7	26.4	20.3	18.7	20.3	26.4	35.7
97.5°	127.5	81.3	69.5	57.7	43.4	35.2	30.2	29.7	30.2	35.2	43.4
100°	125.9	87.4	76.7	66.0	52.8	45.1	41.2	40.7	41.2	45.1	52.8
102.5°	128.1	94.5	84.9	75.3	63.8	56.6	53.3	52.2	53.3	56.6	63.8
105°	132.5	102.8	94.2	85.7	75.3	68.7	65.4	63.8	65.4	68.7	75.3
107.5°	139.6	113.2	105.2	97.3	87.4	80.8	77.5	75.9	77.5	80.8	87.4
110°	149.0	124.2	116.5	108.8	99.5	93.4	90.7	89.0	90.7	93.4	99.5

TEST NUMBER: P1011408

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	158.3	135.8	128.4	120.9	111.6	105.5	102.8	101.1	102.8	105.5	111.6
115°	168.7	147.9	140.4	133.0	123.7	118.2	114.9	112.7	114.9	118.2	123.7
117.5°	179.7	158.9	152.0	145.1	134.7	129.7	127.0	124.2	127.0	129.7	134.7
120°	190.2	170.4	163.6	156.7	146.2	140.7	138.0	136.3	138.0	140.7	146.2
122.5°	201.2	181.9	174.5	167.1	157.2	151.2	148.4	146.8	148.4	151.2	157.2
125°	211.6	192.4	185.0	177.5	167.1	161.1	157.8	156.7	157.8	161.1	167.1
127.5°	221.0	202.3	194.9	187.4	175.9	169.8	166.0	164.3	166.0	169.8	175.9
130°	229.2	211.1	203.6	196.2	184.7	178.1	173.1	171.5	173.1	178.1	184.7
132.5°	236.4	218.8	211.6	204.5	192.9	184.7	179.2	177.0	179.2	184.7	192.9
135°	243.5	226.5	219.0	211.6	200.1	191.8	185.8	183.6	185.8	191.8	200.1
137.5°	248.4	232.0	225.1	218.2	206.7	197.9	191.8	189.6	191.8	197.9	206.7
140°	253.4	237.5	230.6	223.7	212.7	203.9	198.4	195.7	198.4	203.9	212.7
142.5°	257.2	241.9	235.6	229.2	218.2	210.5	204.5	202.3	204.5	210.5	218.2
145°	260.5	246.2	239.9	233.6	224.3	216.0	211.1	209.4	211.1	216.0	224.3
147.5°	263.3	250.1	244.6	239.1	229.8	222.6	217.7	216.6	217.7	222.6	229.8
150°	266.0	253.4	248.4	243.5	235.8	228.7	224.3	223.7	224.3	228.7	235.8
152.5°	267.7	257.2	252.6	247.9	241.3	235.3	230.9	230.9	230.9	235.3	241.3
155°	269.9	260.5	256.6	252.8	246.8	241.3	238.0	238.0	238.0	241.3	246.8
157.5°	271.0	263.3	260.2	257.2	251.7	246.8	244.0	243.5	244.0	246.8	251.7
160°	272.6	266.0	263.2	260.5	256.7	252.3	250.1	250.1	250.1	252.3	256.7
162.5°	273.2	267.7	265.5	263.3	260.0	256.7	255.0	255.0	255.0	256.7	260.0
165°	273.7	269.3	267.4	265.5	263.3	260.5	259.4	260.0	259.4	260.5	263.3
167.5°	273.7	270.4	269.0	267.7	266.0	263.8	263.3	263.8	263.3	263.8	266.0
170°	273.2	270.4	269.8	269.3	268.2	266.6	266.0	267.1	266.0	266.6	268.2
172.5°	273.2	271.0	270.7	270.4	269.9	268.8	268.8	269.3	268.8	268.8	269.9
175°	272.6	271.5	271.2	271.0	271.0	269.9	270.4	271.0	270.4	269.9	271.0
177.5°	272.1	271.5	271.5	271.5	271.5	271.0	271.5	272.1	271.5	271.0	271.5
180°	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5

TEST NUMBER: P1011408

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1539.0	1537.5	1540.5	1531.4	1516.2	1508.7	1487.5	1482.9	1481.4	1482.9	1484.4
5°	1496.6	1495.0	1490.5	1475.3	1457.2	1443.5	1417.8	1416.3	1407.2	1398.1	1402.6
7.5°	1455.7	1449.6	1440.5	1420.8	1396.6	1381.4	1360.2	1345.1	1333.0	1325.4	1319.3
10°	1414.8	1405.7	1396.6	1370.8	1340.5	1317.8	1292.1	1279.9	1266.3	1260.3	1254.2
12.5°	1361.7	1352.7	1336.0	1305.7	1287.5	1258.7	1233.0	1220.9	1213.3	1201.2	1193.6
15°	1319.3	1301.2	1292.1	1260.3	1222.4	1219.4	1172.4	1169.4	1154.2	1154.2	1142.1
17.5°	1270.9	1257.2	1240.6	1208.8	1181.5	1154.2	1130.0	1120.9	1107.3	1104.2	1098.2
20°	1223.9	1205.7	1199.7	1167.9	1139.1	1105.8	1080.0	1070.9	1064.9	1058.8	1063.3
22.5°	1175.4	1160.3	1145.1	1116.4	1095.2	1061.8	1046.7	1037.6	1028.5	1025.5	1027.0
25°	1128.5	1114.8	1099.7	1070.9	1048.2	1020.9	1007.3	1002.8	998.2	998.2	996.7
27.5°	1083.0	1069.4	1055.8	1030.0	1007.3	987.6	977.0	972.5	967.9	970.9	974.0
30°	1036.1	1024.0	1011.8	989.1	970.9	952.8	946.7	943.7	942.2	949.7	949.7
32.5°	993.7	983.1	974.0	952.8	934.6	919.4	914.9	916.4	917.9	922.5	925.5
35°	949.7	942.2	933.1	914.9	899.8	886.1	887.6	887.6	890.7	898.2	904.3
37.5°	910.4	899.8	892.2	877.0	864.9	852.8	857.3	861.9	864.9	874.0	877.0
40°	863.4	858.9	852.8	837.6	827.0	825.5	827.0	830.1	836.1	840.7	845.2
42.5°	825.5	819.5	811.9	799.8	790.7	792.2	793.7	796.7	799.8	807.4	811.9
45°	783.1	778.6	772.5	761.9	754.3	755.9	757.4	757.4	760.4	769.5	772.5
47.5°	736.2	737.7	730.1	719.5	715.0	715.0	715.0	718.0	725.6	728.6	730.1
50°	690.7	687.7	686.2	675.6	672.5	671.0	672.5	674.1	684.7	683.1	687.7
52.5°	642.2	642.2	640.7	634.7	630.1	630.1	627.1	634.7	637.7	640.7	645.3
55°	595.3	590.7	589.2	586.2	580.1	578.6	581.7	590.7	593.8	596.8	601.3
57.5°	543.8	543.8	540.8	536.2	536.2	536.2	536.2	542.3	546.8	549.8	558.9
60°	496.8	490.8	486.2	486.2	486.2	484.7	493.8	493.8	502.9	504.4	507.4
62.5°	440.8	437.8	434.7	436.2	434.7	437.8	440.8	446.8	448.4	452.9	457.4
65°	387.8	387.8	384.7	393.8	387.8	387.8	395.3	395.3	398.4	402.9	409.0
67.5°	336.3	337.8	334.8	334.8	337.8	339.3	340.8	346.9	348.4	354.4	362.0
70°	283.3	286.3	287.8	284.8	287.8	290.8	293.9	295.4	301.4	304.5	309.0
72.5°	236.3	239.3	234.8	236.3	237.8	240.8	242.4	245.4	248.4	257.5	260.5
75°	189.3	187.8	186.3	192.4	189.3	195.4	196.9	196.9	199.9	207.5	210.5
77.5°	145.4	145.4	146.9	143.9	148.4	146.9	148.4	153.0	157.5	157.5	169.7
80°	101.5	104.5	104.5	104.5	106.0	107.5	104.5	112.1	113.6	113.6	118.1
82.5°	65.1	66.6	65.1	68.2	68.2	71.2	69.7	71.2	74.2	77.3	78.8
85°	34.8	34.8	37.9	37.9	36.4	37.9	36.4	37.9	40.9	40.9	42.4
87.5°	12.1	12.1	12.1	12.1	13.6	12.1	13.6	13.6	12.1	12.1	16.7
90°	6.0	6.6	7.1	8.8	10.4	12.1	13.7	13.2	13.7	14.3	14.8
92.5°	28.0	33.0	37.9	55.5	84.6	113.2	102.2	76.4	54.4	42.3	36.8
95°	50.0	60.8	71.5	118.2	200.1	290.2	325.9	264.4	197.9	134.1	105.0
97.5°	57.7	69.5	81.3	127.5	222.6	374.3	501.3	518.3	454.6	343.0	270.4
100°	66.0	76.7	87.4	125.9	207.2	351.8	520.5	628.8	648.1	603.5	539.2
102.5°	75.3	84.9	94.5	128.1	194.0	318.8	484.8	634.3	712.4	721.7	690.9
105°	85.7	94.2	102.8	132.5	189.1	293.0	441.9	599.7	714.6	769.5	780.0
107.5°	97.3	105.2	113.2	139.6	188.0	274.3	404.0	550.2	681.6	767.9	810.8
110°	108.8	116.5	124.2	149.0	190.7	264.4	372.7	504.0	629.9	731.0	800.3

TEST NUMBER: P1011408

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	120.9	128.4	135.8	158.3	196.2	258.9	351.8	463.9	578.8	682.7	762.4
115°	133.0	140.4	147.9	168.7	202.3	258.3	338.0	433.1	534.8	630.5	711.3
117.5°	145.1	152.0	158.9	179.7	210.0	258.9	328.7	412.8	500.7	585.4	659.6
120°	156.7	163.6	170.4	190.2	218.8	261.1	322.7	397.4	474.9	549.1	615.1
122.5°	167.1	174.5	181.9	201.2	227.0	264.9	318.8	384.8	454.6	520.0	579.9
125°	177.5	185.0	192.4	211.6	235.8	268.8	315.5	374.3	437.0	496.9	549.7
127.5°	187.4	194.9	202.3	221.0	243.0	273.2	313.9	364.4	421.0	475.5	523.8
130°	196.2	203.6	211.1	229.2	250.1	277.6	312.2	356.7	406.2	455.7	500.2
132.5°	204.5	211.6	218.8	236.4	256.7	280.9	311.7	349.6	392.5	437.0	477.7
135°	211.6	219.0	226.5	243.5	262.2	284.2	311.1	343.5	380.4	419.4	455.1
137.5°	218.2	225.1	232.0	248.4	266.6	286.4	310.0	338.0	368.8	401.8	433.7
140°	223.7	230.6	237.5	253.4	269.9	288.6	309.5	333.1	358.9	387.0	413.3
142.5°	229.2	235.6	241.9	257.2	273.2	290.2	308.4	328.7	349.6	372.7	394.7
145°	233.6	239.9	246.2	260.5	275.4	290.8	307.3	324.8	342.4	360.6	378.2
147.5°	239.1	244.6	250.1	263.3	277.0	290.8	305.6	321.0	336.4	351.2	366.1
150°	243.5	248.4	253.4	266.0	277.6	290.8	303.4	317.2	329.8	342.4	354.0
152.5°	247.9	252.6	257.2	267.7	278.7	289.1	300.7	312.8	323.8	334.2	344.1
155°	252.8	256.6	260.5	269.9	278.7	288.0	297.4	308.4	317.7	326.5	334.7
157.5°	257.2	260.2	263.3	271.0	279.2	286.4	294.6	303.4	311.1	318.8	325.4
160°	260.5	263.2	266.0	272.6	279.2	285.3	291.3	298.5	305.6	311.7	317.2
162.5°	263.3	265.5	267.7	273.2	278.7	283.1	288.0	293.5	299.0	304.0	308.9
165°	265.5	267.4	269.3	273.7	277.6	280.9	284.7	289.1	293.5	296.8	300.7
167.5°	267.7	269.0	270.4	273.7	277.0	278.7	281.4	284.7	288.6	291.3	293.5
170°	269.3	269.8	270.4	273.2	275.4	276.5	278.1	280.9	283.6	285.3	287.5
172.5°	270.4	270.7	271.0	273.2	274.8	274.8	275.4	277.0	279.2	280.3	282.0
175°	271.0	271.2	271.5	272.6	273.7	273.2	273.2	274.3	275.4	275.9	277.0
177.5°	271.5	271.5	271.5	272.1	273.2	272.1	271.5	272.1	272.6	273.2	273.7
180°	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5

TEST NUMBER: P1011408

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1482.9	1484.4	1478.4	1473.8	1486.0	1478.4	1478.4	1479.9	1476.9	1481.4	1479.9
5°	1399.6	1401.1	1390.5	1393.6	1387.5	1386.0	1384.5	1393.6	1392.0	1390.5	1393.6
7.5°	1317.8	1317.8	1313.3	1310.2	1310.2	1305.7	1311.8	1310.2	1313.3	1313.3	1317.8
10°	1249.7	1252.7	1245.1	1237.5	1236.0	1237.5	1237.5	1239.1	1240.6	1251.2	1249.7
12.5°	1193.6	1189.1	1187.6	1183.0	1175.4	1172.4	1169.4	1186.0	1181.5	1181.5	1181.5
15°	1131.5	1142.1	1140.6	1127.0	1123.9	1130.0	1127.0	1127.0	1142.1	1140.6	1139.1
17.5°	1098.2	1095.2	1092.1	1084.5	1086.1	1084.5	1086.1	1086.1	1095.2	1095.2	1095.2
20°	1060.3	1054.3	1054.3	1051.2	1051.2	1046.7	1052.7	1054.3	1060.3	1060.3	1061.8
22.5°	1027.0	1022.4	1022.4	1020.9	1024.0	1017.9	1024.0	1025.5	1025.5	1030.0	1030.0
25°	998.2	995.2	995.2	998.2	998.2	998.2	998.2	1004.3	999.7	1001.2	999.7
27.5°	972.5	974.0	975.5	977.0	975.5	977.0	978.5	981.5	983.1	981.5	978.5
30°	948.2	952.8	954.3	954.3	957.3	958.8	960.3	960.3	961.9	957.3	960.3
32.5°	930.0	930.0	933.1	934.6	937.6	939.1	939.1	942.2	940.6	936.1	937.6
35°	904.3	904.3	910.4	913.4	917.9	916.4	917.9	917.9	919.4	916.4	911.9
37.5°	878.5	881.6	881.6	887.6	889.1	890.7	889.1	892.2	890.7	887.6	886.1
40°	848.3	846.7	848.3	852.8	854.3	854.3	854.3	857.3	857.3	857.3	855.8
42.5°	810.4	814.9	813.4	818.0	816.4	816.4	819.5	822.5	824.0	819.5	821.0
45°	774.0	774.0	777.1	777.1	778.6	778.6	784.6	781.6	784.6	781.6	783.1
47.5°	734.6	736.2	736.2	737.7	740.7	743.7	740.7	742.2	742.2	743.7	740.7
50°	690.7	690.7	693.7	698.3	704.4	701.3	699.8	705.9	701.3	701.3	698.3
52.5°	645.3	649.8	651.3	655.9	660.4	661.9	663.5	660.4	661.9	657.4	658.9
55°	601.3	602.9	608.9	613.5	618.0	618.0	616.5	618.0	619.5	613.5	613.5
57.5°	557.4	562.0	568.0	568.0	574.1	574.1	572.6	572.6	574.1	569.5	568.0
60°	510.5	515.0	522.6	522.6	531.7	533.2	530.2	527.1	527.1	522.6	524.1
62.5°	460.5	465.0	469.6	477.1	483.2	480.2	486.2	480.2	481.7	472.6	472.6
65°	416.6	418.1	425.6	433.2	433.2	436.2	433.2	434.7	430.2	430.2	424.1
67.5°	365.1	365.1	372.6	380.2	387.8	387.8	387.8	383.2	383.2	378.7	378.7
70°	319.6	318.1	325.7	330.2	334.8	336.3	333.2	331.7	328.7	324.2	322.6
72.5°	263.6	266.6	274.2	277.2	284.8	283.3	290.8	281.7	281.7	274.2	272.7
75°	213.6	216.6	224.2	228.7	233.3	233.3	237.8	233.3	227.2	224.2	222.7
77.5°	169.7	168.1	174.2	181.8	183.3	181.8	184.8	183.3	177.2	177.2	174.2
80°	121.2	125.7	131.8	130.3	136.3	134.8	134.8	131.8	131.8	127.2	130.3
82.5°	80.3	84.8	86.3	84.8	86.3	89.4	90.9	89.4	89.4	86.3	87.9
85°	42.4	42.4	45.4	47.0	45.4	45.4	47.0	51.5	48.5	45.4	48.5
87.5°	13.6	12.1	12.1	13.6	12.1	12.1	13.6	13.6	15.1	15.1	15.1
90°	15.4	15.9	15.4	15.9	16.5	15.9	16.5	15.9	15.4	15.9	15.4
92.5°	34.9	33.0	31.9	29.7	30.2	29.1	30.2	29.7	31.9	33.0	34.9
95°	95.1	85.2	74.8	69.8	66.0	63.8	66.0	69.8	74.8	85.2	95.1
97.5°	239.1	207.8	170.9	150.1	136.9	130.8	136.9	150.1	170.9	207.8	239.1
100°	500.2	461.2	405.7	365.5	344.1	344.6	344.1	365.5	405.7	461.2	500.2
102.5°	669.8	648.6	608.5	578.8	561.8	545.8	561.8	578.8	608.5	648.6	669.8
105°	772.8	765.7	740.4	719.5	701.9	699.2	701.9	719.5	740.4	765.7	772.8
107.5°	818.2	825.6	822.3	812.4	805.3	799.2	805.3	812.4	822.3	825.6	818.2
110°	819.6	838.8	854.2	858.6	857.5	856.4	857.5	858.6	854.2	838.8	819.6

TEST NUMBER: P1011408

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	788.5	814.6	845.9	861.9	867.4	867.9	867.4	861.9	845.9	814.6	788.5
115°	741.2	771.2	812.4	836.6	847.6	850.3	847.6	836.6	812.4	771.2	741.2
117.5°	690.7	721.7	764.6	791.5	808.0	811.8	808.0	791.5	764.6	721.7	690.7
120°	642.8	670.6	714.0	744.8	758.0	761.3	758.0	744.8	714.0	670.6	642.8
122.5°	605.2	630.5	667.8	694.8	709.6	714.0	709.6	694.8	667.8	630.5	605.2
125°	571.7	593.6	628.8	653.0	666.7	670.6	666.7	653.0	628.8	593.6	571.7
127.5°	544.2	564.5	596.4	617.3	629.9	633.2	629.9	617.3	596.4	564.5	544.2
130°	518.9	537.6	566.7	586.5	598.0	602.4	598.0	586.5	566.7	537.6	518.9
132.5°	495.2	512.8	539.8	559.6	569.4	572.2	569.4	559.6	539.8	512.8	495.2
135°	470.8	486.5	513.4	529.9	539.8	543.6	539.8	529.9	513.4	486.5	470.8
137.5°	447.7	461.7	484.8	501.8	510.1	513.4	510.1	501.8	484.8	461.7	447.7
140°	425.2	437.0	457.9	473.3	482.1	481.5	482.1	473.3	457.9	437.0	425.2
142.5°	404.5	414.4	431.5	444.7	452.4	451.8	452.4	444.7	431.5	414.4	404.5
145°	386.2	394.1	407.8	419.4	423.8	424.9	423.8	419.4	407.8	394.1	386.2
147.5°	371.8	377.6	388.6	396.9	401.3	401.8	401.3	396.9	388.6	377.6	371.8
150°	359.2	364.4	372.7	378.7	382.0	382.0	382.0	378.7	372.7	364.4	359.2
152.5°	348.2	352.3	358.4	363.9	365.5	365.5	365.5	363.9	358.4	352.3	348.2
155°	338.0	341.3	346.3	350.7	351.8	352.3	351.8	350.7	346.3	341.3	338.0
157.5°	328.2	330.9	335.3	338.6	339.7	339.7	339.7	338.6	335.3	330.9	328.2
160°	319.1	321.0	324.8	328.1	328.1	327.6	328.1	328.1	324.8	321.0	319.1
162.5°	310.5	312.2	314.4	317.2	317.2	316.6	317.2	317.2	314.4	312.2	310.5
165°	302.0	303.4	305.6	307.8	307.3	307.3	307.3	307.8	305.6	303.4	302.0
167.5°	294.6	295.7	296.8	298.5	297.9	297.9	297.9	298.5	296.8	295.7	294.6
170°	288.0	288.6	289.1	290.2	289.7	289.7	289.7	290.2	289.1	288.6	288.0
172.5°	282.2	282.5	282.5	283.6	282.5	282.0	282.5	283.6	282.5	282.5	282.2
175°	277.0	277.0	277.0	277.6	277.0	276.5	277.0	277.6	277.0	277.0	277.0
177.5°	273.7	273.7	273.2	273.7	272.6	272.6	272.6	273.7	273.2	273.7	273.7
180°	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5

TEST NUMBER: P1011408

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1484.4	1487.5	1489.0	1482.9	1478.4	1486.0	1496.6	1504.1	1510.2	1517.8	1522.3
5°	1396.6	1407.2	1407.2	1410.2	1414.8	1422.3	1442.0	1455.7	1467.8	1476.9	1484.4
7.5°	1322.4	1329.9	1334.5	1342.1	1349.6	1360.2	1383.0	1402.6	1420.8	1431.4	1443.5
10°	1255.7	1261.8	1269.3	1273.9	1287.5	1302.7	1331.4	1348.1	1369.3	1386.0	1401.1
12.5°	1192.1	1213.3	1217.8	1216.3	1228.4	1245.1	1273.9	1299.6	1322.4	1339.0	1355.7
15°	1146.7	1154.2	1163.3	1161.8	1187.6	1192.1	1216.3	1246.6	1276.9	1287.5	1302.7
17.5°	1096.7	1108.8	1117.9	1122.4	1130.0	1146.7	1169.4	1192.1	1231.5	1233.0	1272.4
20°	1057.3	1069.4	1075.5	1081.5	1086.1	1105.8	1125.4	1151.2	1183.0	1199.7	1220.9
22.5°	1031.5	1037.6	1042.1	1046.7	1052.7	1063.3	1087.6	1116.4	1137.6	1155.7	1169.4
25°	1001.2	1007.3	1013.4	1016.4	1020.9	1027.0	1045.2	1067.9	1098.2	1110.3	1123.9
27.5°	980.0	980.0	983.1	983.1	989.1	995.2	1008.8	1030.0	1054.3	1069.4	1087.6
30°	957.3	955.8	957.3	955.8	954.3	963.4	975.5	993.7	1010.3	1028.5	1040.6
32.5°	934.6	933.1	933.1	934.6	928.5	933.1	939.1	955.8	974.0	983.1	996.7
35°	910.4	907.3	907.3	907.3	904.3	901.3	907.3	922.5	934.6	946.7	957.3
37.5°	886.1	881.6	881.6	878.5	875.5	871.0	871.0	883.1	899.8	904.3	917.9
40°	852.8	852.8	849.8	848.3	845.2	842.2	837.6	848.3	863.4	867.9	878.5
42.5°	819.5	814.9	813.4	813.4	813.4	808.9	805.8	813.4	822.5	830.1	836.1
45°	781.6	778.6	780.1	778.6	775.5	774.0	772.5	775.5	786.1	789.2	796.7
47.5°	740.7	739.2	739.2	737.7	736.2	737.7	731.6	739.2	742.2	745.2	751.3
50°	698.3	696.8	695.3	693.7	693.7	695.3	693.7	693.7	699.8	702.8	708.9
52.5°	655.9	651.3	651.3	649.8	649.8	646.8	649.8	651.3	654.4	657.4	660.4
55°	610.4	610.4	605.9	605.9	602.9	602.9	604.4	602.9	608.9	612.0	612.0
57.5°	566.5	560.5	562.0	558.9	555.9	554.4	554.4	557.4	560.5	560.5	563.5
60°	519.6	513.5	512.0	505.9	509.0	504.4	505.9	505.9	512.0	509.0	512.0
62.5°	472.6	465.0	460.5	457.4	457.4	459.0	455.9	454.4	457.4	460.5	466.5
65°	422.6	418.1	413.5	409.0	409.0	407.5	410.5	405.9	404.4	405.9	409.0
67.5°	371.1	366.6	362.0	357.5	359.0	354.4	351.4	356.0	352.9	354.4	357.5
70°	321.1	318.1	309.0	306.0	304.5	306.0	304.5	301.4	306.0	304.5	306.0
72.5°	271.1	268.1	263.6	256.0	256.0	254.5	253.0	253.0	251.4	251.4	251.4
75°	222.7	216.6	212.1	210.5	207.5	206.0	204.5	201.5	203.0	204.5	201.5
77.5°	172.7	165.1	163.6	163.6	159.0	159.0	160.6	159.0	157.5	157.5	157.5
80°	127.2	121.2	121.2	118.1	115.1	115.1	115.1	115.1	113.6	112.1	113.6
82.5°	81.8	80.3	78.8	78.8	81.8	75.7	78.8	77.3	75.7	75.7	74.2
85°	45.4	47.0	45.4	47.0	43.9	45.4	45.4	45.4	43.9	45.4	42.4
87.5°	16.7	16.7	16.7	18.2	18.2	18.2	18.2	18.2	19.7	18.2	18.2
90°	14.8	14.3	13.7	13.2	13.7	12.1	10.4	8.8	7.1	6.6	6.0
92.5°	36.8	42.3	54.4	76.4	102.2	113.2	84.6	55.5	37.9	33.0	28.0
95°	105.0	134.1	197.9	264.4	325.9	290.2	200.1	118.2	71.5	60.8	50.0
97.5°	270.4	343.0	454.6	518.3	501.3	374.3	222.6	127.5	81.3	69.5	57.7
100°	539.2	603.5	648.1	628.8	520.5	351.8	207.2	125.9	87.4	76.7	66.0
102.5°	690.9	721.7	712.4	634.3	484.8	318.8	194.0	128.1	94.5	84.9	75.3
105°	780.0	769.5	714.6	599.7	441.9	293.0	189.1	132.5	102.8	94.2	85.7
107.5°	810.8	767.9	681.6	550.2	404.0	274.3	188.0	139.6	113.2	105.2	97.3
110°	800.3	731.0	629.9	504.0	372.7	264.4	190.7	149.0	124.2	116.5	108.8

TEST NUMBER: P1011408

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	762.4	682.7	578.8	463.9	351.8	258.9	196.2	158.3	135.8	128.4	120.9
115°	711.3	630.5	534.8	433.1	338.0	258.3	202.3	168.7	147.9	140.4	133.0
117.5°	659.6	585.4	500.7	412.8	328.7	258.9	210.0	179.7	158.9	152.0	145.1
120°	615.1	549.1	474.9	397.4	322.7	261.1	218.8	190.2	170.4	163.6	156.7
122.5°	579.9	520.0	454.6	384.8	318.8	264.9	227.0	201.2	181.9	174.5	167.1
125°	549.7	496.9	437.0	374.3	315.5	268.8	235.8	211.6	192.4	185.0	177.5
127.5°	523.8	475.5	421.0	364.4	313.9	273.2	243.0	221.0	202.3	194.9	187.4
130°	500.2	455.7	406.2	356.7	312.2	277.6	250.1	229.2	211.1	203.6	196.2
132.5°	477.7	437.0	392.5	349.6	311.7	280.9	256.7	236.4	218.8	211.6	204.5
135°	455.1	419.4	380.4	343.5	311.1	284.2	262.2	243.5	226.5	219.0	211.6
137.5°	433.7	401.8	368.8	338.0	310.0	286.4	266.6	248.4	232.0	225.1	218.2
140°	413.3	387.0	358.9	333.1	309.5	288.6	269.9	253.4	237.5	230.6	223.7
142.5°	394.7	372.7	349.6	328.7	308.4	290.2	273.2	257.2	241.9	235.6	229.2
145°	378.2	360.6	342.4	324.8	307.3	290.8	275.4	260.5	246.2	239.9	233.6
147.5°	366.1	351.2	336.4	321.0	305.6	290.8	277.0	263.3	250.1	244.6	239.1
150°	354.0	342.4	329.8	317.2	303.4	290.8	277.6	266.0	253.4	248.4	243.5
152.5°	344.1	334.2	323.8	312.8	300.7	289.1	278.7	267.7	257.2	252.6	247.9
155°	334.7	326.5	317.7	308.4	297.4	288.0	278.7	269.9	260.5	256.6	252.8
157.5°	325.4	318.8	311.1	303.4	294.6	286.4	279.2	271.0	263.3	260.2	257.2
160°	317.2	311.7	305.6	298.5	291.3	285.3	279.2	272.6	266.0	263.2	260.5
162.5°	308.9	304.0	299.0	293.5	288.0	283.1	278.7	273.2	267.7	265.5	263.3
165°	300.7	296.8	293.5	289.1	284.7	280.9	277.6	273.7	269.3	267.4	265.5
167.5°	293.5	291.3	288.6	284.7	281.4	278.7	277.0	273.7	270.4	269.0	267.7
170°	287.5	285.3	283.6	280.9	278.1	276.5	275.4	273.2	270.4	269.8	269.3
172.5°	282.0	280.3	279.2	277.0	275.4	274.8	274.8	273.2	271.0	270.7	270.4
175°	277.0	275.9	275.4	274.3	273.2	273.2	273.7	272.6	271.5	271.2	271.0
177.5°	273.7	273.2	272.6	272.1	271.5	272.1	273.2	272.1	271.5	271.5	271.5
180°	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5

TEST NUMBER: P1011408

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1563.2	1563.2	1563.2	1563.2
2.5°	1529.9	1534.4	1549.6	1567.7
5°	1499.6	1511.7	1532.9	1561.7
7.5°	1466.3	1484.4	1514.7	1551.1
10°	1428.4	1454.1	1492.0	1537.5
12.5°	1387.5	1420.8	1469.3	1516.2
15°	1361.7	1395.1	1439.0	1490.5
17.5°	1311.8	1351.1	1396.6	1469.3
20°	1260.3	1304.2	1363.3	1436.0
22.5°	1220.9	1267.8	1323.9	1401.1
25°	1173.9	1222.4	1283.0	1363.3
27.5°	1123.9	1172.4	1240.6	1325.4
30°	1086.1	1133.0	1198.2	1289.0
32.5°	1040.6	1086.1	1154.2	1249.7
35°	989.1	1040.6	1105.8	1202.7
37.5°	949.7	996.7	1064.9	1157.3
40°	907.3	948.2	1014.9	1105.8
42.5°	861.9	907.3	964.9	1055.8
45°	819.5	852.8	911.9	998.2
47.5°	774.0	811.9	857.3	924.0
50°	725.6	757.4	807.4	852.8
52.5°	678.6	704.4	746.8	781.6
55°	628.6	654.4	686.2	707.4
57.5°	581.7	599.8	621.0	634.7
60°	524.1	542.3	555.9	569.5
62.5°	472.6	486.2	493.8	501.4
65°	419.6	427.2	431.7	437.8
67.5°	362.0	369.6	371.1	380.2
70°	309.0	310.5	313.5	318.1
72.5°	259.0	262.0	260.5	263.6
75°	207.5	210.5	207.5	210.5
77.5°	157.5	160.6	160.6	165.1
80°	113.6	115.1	116.6	116.6
82.5°	74.2	78.8	75.7	77.3
85°	42.4	43.9	43.9	45.4
87.5°	19.7	21.2	19.7	22.7
90°	4.9	3.3	2.2	1.1
92.5°	22.5	17.6	12.1	8.2
95°	35.7	26.4	20.3	18.7
97.5°	43.4	35.2	30.2	29.7
100°	52.8	45.1	41.2	40.7
102.5°	63.8	56.6	53.3	52.2
105°	75.3	68.7	65.4	63.8
107.5°	87.4	80.8	77.5	75.9
110°	99.5	93.4	90.7	89.0

TEST NUMBER: P1011408

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	111.6	105.5	102.8	101.1
115°	123.7	118.2	114.9	112.7
117.5°	134.7	129.7	127.0	124.2
120°	146.2	140.7	138.0	136.3
122.5°	157.2	151.2	148.4	146.8
125°	167.1	161.1	157.8	156.7
127.5°	175.9	169.8	166.0	164.3
130°	184.7	178.1	173.1	171.5
132.5°	192.9	184.7	179.2	177.0
135°	200.1	191.8	185.8	183.6
137.5°	206.7	197.9	191.8	189.6
140°	212.7	203.9	198.4	195.7
142.5°	218.2	210.5	204.5	202.3
145°	224.3	216.0	211.1	209.4
147.5°	229.8	222.6	217.7	216.6
150°	235.8	228.7	224.3	223.7
152.5°	241.3	235.3	230.9	230.9
155°	246.8	241.3	238.0	238.0
157.5°	251.7	246.8	244.0	243.5
160°	256.7	252.3	250.1	250.1
162.5°	260.0	256.7	255.0	255.0
165°	263.3	260.5	259.4	260.0
167.5°	266.0	263.8	263.3	263.8
170°	268.2	266.6	266.0	267.1
172.5°	269.9	268.8	268.8	269.3
175°	271.0	269.9	270.4	271.0
177.5°	271.5	271.0	271.5	272.1
180°	271.5	271.5	271.5	271.5

(END OF REPORT)