

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011477

Luminaire Tested: S123DIP-B340D1025UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011477
REPORT IS A COMBINATION OF REPORTS P989654 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D1025UB35-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5110.0 lumens
Efficiency: N/A
Efficacy: 123.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011477

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1011477

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	36	36	28
1	93	89	85	82	83	80	77	74	62	60	58	46	45	44	32	31	30	30	30	24
2	85	78	72	67	76	70	65	61	55	51	49	41	39	37	28	27	26	26	26	20
3	77	68	61	56	69	61	56	51	48	44	41	36	34	31	25	23	22	22	22	17
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	21	19	19	19	15
5	65	54	46	40	58	48	42	37	38	34	30	29	26	23	20	18	17	17	17	13
6	60	48	40	35	53	43	37	32	34	30	26	26	23	20	18	16	15	15	15	11
7	55	43	36	30	49	39	32	28	31	26	23	24	20	18	17	15	13	13	13	10
8	51	39	32	27	45	35	29	24	28	24	20	22	18	16	15	13	12	12	12	9
9	47	36	28	24	42	32	26	22	26	21	18	20	17	14	14	12	10	10	10	8
10	44	33	26	21	39	29	23	19	24	19	16	18	15	13	13	11	9	9	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5061	5061	5061	5061
5°	5064	5831	5079	4352
10°	5032	7056	5037	3800
15°	4962	8368	5002	3421
20°	4903	9634	4913	3148
25°	4813	9878	4824	3005
30°	4750	8161	4750	2912
35°	4671	5458	4641	2829
40°	4577	3940	4521	2703
45°	4458	3121	4331	2547
50°	4171	2650	4023	2392
55°	3856	2329	3698	2220
60°	3535	2028	3347	2040
65°	3184	1736	3029	1799
70°	2818	1441	2630	1516
75°	2408	1086	2252	1171
80°	1906	726	1754	768
85°	1316	332	1047	304

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 8162 cd/sqm

TEST NUMBER: P1011477

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.2	0.9
10°-20°	148.5	2.9
20°-30°	249.9	4.9
30°-40°	282.4	5.5
40°-50°	252.9	4.9
50°-60°	204.2	4.0
60°-70°	142.3	2.8
70°-80°	74.7	1.5
80°-90°	20.6	0.4
90°-100°	266.1	5.2
100°-110°	779.0	15.2
110°-120°	760.7	14.9
120°-130°	605.8	11.9
130°-140°	478.0	9.4
140°-150°	356.6	7.0
150°-160°	248.6	4.9
160°-170°	146.0	2.9
170°-180°	47.5	0.9
0°-30°	444.6	8.7
0°-40°	727.0	14.2
0°-60°	1184.1	23.2
0°-90°	1421.7	27.8
90°-120°	1805.8	35.3
90°-150°	3246.1	63.5
90°-180°	3688.0	72.2
0°-180°	5110.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	470	470	470	470	470	
5°	470	558	471	417	470	45
15°	448	831	452	340	448	127
25°	410	987	411	300	410	189
35°	362	532	359	276	362	226
45°	300	287	292	234	300	230
55°	213	195	204	186	213	191
65°	132	127	125	131	132	131
75°	63	65	59	70	63	68
85°	14	15	11	14	14	16
90°	2	29	2	29	2	4
95°	34	115	34	115	34	36
105°	115	1262	115	1262	115	122
115°	204	1536	204	1536	204	201
125°	283	1211	283	1211	283	251
135°	332	982	332	982	332	256
145°	378	767	378	767	378	237
155°	430	636	430	636	430	198
165°	470	555	470	555	470	132
175°	489	499	489	499	489	46
180°	490	490	490	490	490	

TEST NUMBER: P1011477

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	471.5	475.2	477.0	479.7	482.5	486.6	487.9	490.2	489.3	491.1	492.0
5°	469.7	476.1	481.5	488.4	494.8	499.3	503.9	511.2	516.6	517.5	521.6
7.5°	466.5	475.6	485.2	494.8	507.1	514.3	522.5	532.6	540.8	554.0	559.0
10°	462.4	475.2	488.8	502.0	518.9	530.3	540.3	557.2	574.0	587.7	600.4
12.5°	456.0	472.0	489.7	509.3	531.2	544.4	558.1	580.4	605.9	626.9	640.5
15°	448.3	468.3	491.1	512.1	536.2	560.8	575.4	600.4	636.9	656.5	691.6
17.5°	441.9	462.4	485.2	518.0	550.8	575.4	585.9	631.9	656.9	689.7	729.4
20°	431.9	457.9	487.0	519.8	562.2	577.2	598.6	645.1	676.1	718.9	767.6
22.5°	421.4	449.2	484.3	518.4	565.8	581.8	610.9	647.8	697.0	739.4	793.2
25°	410.0	440.1	475.6	516.2	562.6	585.9	613.2	658.8	712.1	765.4	815.0
27.5°	398.6	431.4	468.3	508.9	554.0	581.3	608.6	656.0	724.4	782.2	845.5
30°	387.7	420.5	457.4	498.9	546.2	572.7	598.6	657.9	733.9	799.1	862.9
32.5°	375.8	409.6	448.3	482.9	530.7	559.0	588.1	657.9	739.9	809.1	867.4
35°	361.7	396.4	429.6	464.2	511.6	543.0	575.8	653.3	745.3	812.3	848.3
37.5°	348.1	378.6	407.3	441.0	490.7	524.4	562.2	647.8	742.6	798.6	808.6
40°	332.6	363.1	386.3	417.8	470.2	509.3	547.6	640.5	730.7	766.3	737.1
42.5°	317.5	341.7	361.7	392.3	449.2	487.5	528.9	627.3	707.5	714.8	649.2
45°	300.2	317.5	335.3	369.9	426.4	465.6	511.6	608.2	670.2	649.2	566.3
47.5°	277.9	293.4	313.0	344.9	402.3	442.8	486.6	583.6	615.9	572.2	481.5
50°	256.5	269.7	287.9	318.9	376.8	416.4	462.9	544.9	560.8	492.0	415.0
52.5°	235.1	245.1	262.9	293.8	351.7	390.0	432.3	505.2	496.1	422.3	354.0
55°	212.8	221.4	238.3	268.8	322.5	359.0	399.5	456.5	432.8	362.6	308.0
57.5°	190.9	200.0	217.3	242.8	293.4	328.9	361.3	405.9	370.4	314.3	266.1
60°	171.3	179.0	192.3	217.3	263.3	292.0	321.6	352.2	322.5	268.3	231.4
62.5°	150.8	158.1	170.4	193.2	232.8	258.3	282.0	307.1	274.3	234.6	201.8
65°	131.7	137.6	149.0	169.9	202.3	223.2	242.4	259.7	233.3	196.8	172.2
67.5°	114.3	119.4	128.9	147.6	174.9	190.0	205.5	220.0	197.7	168.6	147.6
70°	95.7	99.8	108.4	122.1	144.0	159.5	170.8	181.8	161.7	138.5	124.4
72.5°	79.3	83.4	88.8	103.0	118.0	127.6	139.9	145.8	134.4	115.3	101.1
75°	63.3	66.5	71.5	80.6	94.8	101.1	108.9	113.4	103.0	90.2	81.5
77.5°	49.7	51.0	54.7	61.0	70.6	77.9	83.8	86.6	79.3	71.1	63.8
80°	35.1	36.9	39.6	45.1	52.4	54.7	58.3	61.5	56.9	49.7	45.1
82.5°	23.2	25.5	26.9	29.2	33.7	36.4	37.4	40.1	36.0	33.3	31.4
85°	13.7	14.6	15.0	16.4	18.7	20.0	21.4	21.9	21.0	20.5	18.7
87.5°	6.8	6.8	6.8	7.7	8.2	9.1	9.6	9.6	9.6	9.1	8.7
90°	2.0	4.0	6.0	8.9	10.9	11.9	12.9	15.9	18.9	21.8	24.8
92.5°	14.9	21.8	31.8	40.7	50.6	59.6	68.5	100.2	152.9	204.5	184.6
95°	33.7	36.7	47.6	64.5	90.3	109.6	129.0	213.4	361.3	524.1	588.6
97.5°	53.6	54.6	63.5	78.4	104.2	125.6	146.9	230.3	402.0	675.9	905.2
100°	73.4	74.4	81.4	95.3	119.1	138.4	157.8	227.3	374.2	635.2	940.0
102.5°	94.3	96.3	102.2	115.1	136.0	153.4	170.7	231.3	350.4	575.7	875.4
105°	115.1	118.1	124.1	136.0	154.8	170.2	185.6	239.2	341.4	529.0	798.0
107.5°	137.0	140.0	145.9	157.8	175.7	190.1	204.5	252.1	339.5	495.3	729.5
110°	160.8	163.8	168.7	179.7	196.5	210.4	224.3	269.0	344.4	477.4	673.0

TEST NUMBER: P1011477

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	182.6	185.6	190.6	201.5	218.4	231.8	245.2	285.9	354.3	467.5	635.2
115°	203.5	207.4	213.4	223.3	240.2	253.6	267.0	304.7	365.3	466.5	610.4
117.5°	224.3	229.3	234.2	243.2	262.0	274.4	286.9	324.6	379.2	467.5	593.6
120°	246.2	249.1	254.1	264.0	282.9	295.3	307.7	343.4	395.0	471.5	582.6
122.5°	265.0	268.0	273.0	283.9	301.7	315.1	328.5	363.3	409.9	478.4	575.7
125°	282.9	284.9	290.8	301.7	320.6	334.0	347.4	382.1	425.8	485.4	569.7
127.5°	296.8	299.8	306.7	317.6	338.5	351.9	365.3	399.0	438.7	493.3	566.8
130°	309.7	312.7	321.6	333.5	354.3	367.7	381.1	413.9	451.6	501.2	563.8
132.5°	319.6	323.6	333.5	348.4	369.2	382.1	395.0	426.8	463.5	507.2	562.8
135°	331.5	335.5	346.4	361.3	382.1	395.5	408.9	439.7	473.5	513.2	561.8
137.5°	342.4	346.4	357.3	373.2	394.0	406.4	418.9	448.6	481.4	517.1	559.8
140°	353.4	358.3	368.2	384.1	404.0	416.4	428.8	457.6	487.3	521.1	558.8
142.5°	365.3	369.2	380.2	394.0	413.9	425.3	436.7	464.5	493.3	524.1	556.8
145°	378.2	381.1	390.1	405.0	421.8	433.2	444.7	470.5	497.3	525.1	554.8
147.5°	391.1	393.1	402.0	414.9	431.8	441.7	451.6	475.4	500.3	525.1	551.9
150°	404.0	405.0	412.9	425.8	439.7	448.6	457.6	480.4	501.2	525.1	547.9
152.5°	416.9	416.9	424.8	435.7	447.6	456.0	464.5	483.4	503.2	522.1	542.9
155°	429.8	429.8	435.7	445.7	456.6	463.6	470.5	487.3	503.2	520.1	537.0
157.5°	439.7	440.7	445.7	454.6	464.5	470.0	475.4	489.3	504.2	517.1	532.0
160°	451.6	451.6	455.6	463.5	470.5	475.4	480.4	492.3	504.2	515.1	526.1
162.5°	460.5	460.5	463.5	469.5	475.4	479.4	483.4	493.3	503.2	511.2	520.1
165°	469.5	468.5	470.5	475.4	479.4	482.9	486.4	494.3	501.2	507.2	514.1
167.5°	476.4	475.4	476.4	480.4	483.4	485.8	488.3	494.3	500.3	503.2	508.2
170°	482.4	480.4	481.4	484.4	486.4	487.4	488.3	493.3	497.3	499.3	502.2
172.5°	486.4	485.4	485.4	487.3	488.3	488.8	489.3	493.3	496.3	496.3	497.3
175°	489.3	488.3	487.3	489.3	489.3	489.8	490.3	492.3	494.3	493.3	493.3
177.5°	491.3	490.3	489.3	490.3	490.3	490.3	490.3	491.3	493.3	491.3	490.3
180°	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3

TEST NUMBER: P1011477

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	495.2	496.1	499.3	501.6	506.1	505.7	505.7	505.2	503.9	506.1	507.5
5°	529.8	537.6	538.5	548.5	549.0	553.1	555.8	553.5	559.0	558.5	554.4
7.5°	572.7	583.1	588.1	597.7	608.6	605.9	616.4	618.2	617.3	621.9	625.0
10°	619.6	637.8	650.6	668.3	672.9	675.6	682.5	688.4	700.2	691.1	697.0
12.5°	673.3	686.6	703.4	731.7	745.8	754.9	758.1	762.2	770.4	765.4	765.8
15°	718.4	736.2	764.9	800.0	804.1	815.5	812.7	837.3	849.2	831.4	841.4
17.5°	765.4	789.1	823.2	853.7	871.1	878.8	886.1	909.8	908.9	906.1	908.4
20°	795.4	834.2	876.5	917.1	922.1	928.0	947.6	957.6	955.8	963.5	968.6
22.5°	837.8	878.8	923.9	950.8	962.2	969.0	984.5	990.9	993.6	995.4	992.2
25°	873.3	917.1	950.3	974.0	980.9	984.5	989.5	991.3	990.0	986.8	989.5
27.5°	897.5	932.6	955.3	966.3	962.6	956.7	947.1	940.8	926.6	919.8	928.0
30°	907.5	923.0	929.8	911.6	893.4	878.8	860.6	826.9	800.4	808.2	797.7
32.5°	891.6	881.5	848.7	801.8	787.7	764.0	712.5	672.9	674.3	653.3	662.0
35°	844.6	799.1	737.1	666.1	647.4	634.6	578.1	569.5	551.2	531.7	537.1
37.5°	761.7	695.2	620.0	567.6	539.9	512.1	480.2	461.0	450.1	441.9	448.3
40°	660.6	579.5	517.5	470.6	446.9	429.2	407.3	388.2	375.8	374.5	376.8
42.5°	561.3	492.9	436.0	391.3	383.6	362.6	348.5	333.5	329.8	323.9	327.1
45°	475.2	419.6	372.7	336.2	327.1	321.6	304.3	294.8	290.7	287.0	292.5
47.5°	412.8	354.4	320.3	298.4	289.3	280.2	270.6	264.2	261.0	261.5	261.0
50°	352.6	309.8	279.7	262.9	257.4	251.0	243.3	239.2	237.8	233.7	236.9
52.5°	303.4	272.4	251.5	235.5	231.4	226.9	220.5	218.2	215.0	214.1	214.1
55°	263.8	239.6	222.8	212.3	207.3	203.6	200.0	197.3	195.0	195.0	195.0
57.5°	232.8	211.8	199.5	190.4	188.6	185.0	180.9	180.9	177.7	177.2	178.6
60°	206.4	187.7	178.1	170.4	167.7	166.7	162.6	162.6	161.7	159.5	161.3
62.5°	179.5	165.8	157.6	151.7	149.0	149.0	145.8	143.5	143.5	144.0	143.1
65°	154.9	144.9	137.6	133.0	131.7	129.8	129.4	127.6	126.2	126.6	126.2
67.5°	133.0	125.3	120.3	116.6	114.3	113.4	112.1	112.1	111.2	111.6	109.3
70°	113.4	105.7	101.6	97.9	97.0	97.0	95.2	95.7	94.8	96.1	95.2
72.5°	93.4	87.5	84.3	82.9	82.0	81.5	80.6	79.7	79.3	80.2	79.7
75°	75.6	70.6	68.3	67.4	66.5	66.5	66.1	65.6	65.1	65.1	65.1
77.5°	58.8	55.6	52.8	53.8	52.4	52.8	51.5	51.5	51.9	51.5	51.5
80°	43.3	41.0	41.0	40.1	38.3	39.2	39.2	37.8	37.4	38.3	36.9
82.5°	28.7	28.2	27.3	26.9	26.0	26.4	26.0	25.5	25.1	26.0	25.1
85°	16.9	16.9	16.4	15.5	16.4	15.9	15.5	15.5	15.0	15.0	15.0
87.5°	8.7	7.7	7.7	7.3	7.7	6.8	7.3	6.8	6.4	6.8	6.4
90°	23.8	24.8	25.8	26.8	27.8	28.8	27.8	28.8	29.8	28.8	29.8
92.5°	138.0	98.3	76.4	66.5	63.0	59.6	57.6	53.6	54.6	52.6	54.6
95°	477.4	357.3	242.2	189.6	171.7	153.8	135.0	126.1	119.1	115.1	119.1
97.5°	936.0	820.9	619.4	488.3	431.8	375.2	308.7	271.0	247.1	236.2	247.1
100°	1135.5	1170.2	1089.8	973.7	903.2	832.8	732.5	660.1	621.3	622.3	621.3
102.5°	1145.4	1286.4	1303.2	1247.7	1209.4	1171.2	1098.8	1045.2	1014.4	985.6	1014.4
105°	1082.9	1290.3	1389.6	1408.4	1395.5	1382.6	1337.0	1299.3	1267.5	1262.5	1267.5
107.5°	993.6	1230.8	1386.6	1464.0	1477.4	1490.8	1484.9	1467.0	1454.1	1443.2	1454.1
110°	910.2	1137.5	1320.1	1445.2	1480.0	1514.7	1542.4	1550.4	1548.4	1546.4	1548.4

TEST NUMBER: P1011477

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	837.7	1045.2	1232.8	1376.7	1423.8	1471.0	1527.6	1556.3	1566.3	1567.3	1566.3
115°	782.1	965.8	1138.5	1284.4	1338.5	1392.6	1467.0	1510.7	1530.5	1535.5	1530.5
117.5°	745.4	904.2	1057.1	1191.1	1247.2	1303.2	1380.7	1429.3	1459.1	1466.0	1459.1
120°	717.6	857.6	991.6	1110.7	1160.8	1210.9	1289.3	1344.9	1368.7	1374.7	1368.7
122.5°	694.8	820.9	939.0	1047.2	1092.8	1138.5	1206.0	1254.6	1281.4	1289.3	1281.4
125°	675.9	789.1	897.3	992.6	1032.3	1072.0	1135.5	1179.2	1204.0	1210.9	1204.0
127.5°	658.1	760.3	858.6	945.9	982.6	1019.4	1076.9	1114.6	1137.5	1143.4	1137.5
130°	644.2	733.5	822.8	903.2	937.0	970.7	1023.3	1059.1	1079.9	1087.8	1079.9
132.5°	631.3	708.7	789.1	862.5	894.3	926.1	974.7	1010.4	1028.3	1033.3	1028.3
135°	620.4	686.9	757.3	821.8	850.1	878.4	927.1	956.8	974.7	981.6	974.7
137.5°	610.4	666.0	725.6	783.1	808.4	833.8	875.4	906.2	921.1	927.1	921.1
140°	601.5	648.1	698.8	746.4	767.8	789.1	826.8	854.6	870.5	869.5	870.5
142.5°	593.6	631.3	673.0	712.7	730.6	748.4	779.2	803.0	816.9	815.9	816.9
145°	586.6	618.4	651.1	682.9	697.3	711.7	736.5	757.3	765.3	767.3	765.3
147.5°	579.7	607.4	634.2	661.0	671.4	681.9	701.7	716.6	724.6	725.6	724.6
150°	572.7	595.5	618.4	639.2	648.7	658.1	673.0	683.9	689.8	689.8	689.8
152.5°	564.8	584.6	603.5	621.3	628.8	636.2	647.2	657.1	660.1	660.1	660.1
155°	556.8	573.7	589.6	604.5	610.4	616.4	625.3	633.3	635.2	636.2	635.2
157.5°	547.9	561.8	575.7	587.6	592.6	597.5	605.5	611.4	613.4	613.4	613.4
160°	539.0	551.9	562.8	572.7	576.2	579.7	586.6	592.6	592.6	591.6	592.6
162.5°	530.0	540.0	548.9	557.8	560.8	563.8	567.7	572.7	572.7	571.7	572.7
165°	522.1	530.0	536.0	542.9	545.4	547.9	551.9	555.8	554.8	554.8	554.8
167.5°	514.1	521.1	526.1	530.0	532.0	534.0	536.0	539.0	538.0	538.0	538.0
170°	507.2	512.2	515.1	519.1	520.1	521.1	522.1	524.1	523.1	523.1	523.1
172.5°	500.3	504.2	506.2	509.2	509.7	510.2	510.2	512.2	510.2	509.2	510.2
175°	495.3	497.3	498.3	500.3	500.3	500.3	500.3	501.2	500.3	499.3	500.3
177.5°	491.3	492.3	493.3	494.3	494.3	494.3	493.3	494.3	492.3	492.3	492.3
180°	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3

TEST NUMBER: P1011477

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	503.9	505.2	501.6	500.7	500.7	502.5	501.1	488.8	491.1	488.4	487.5
5°	559.4	556.7	553.1	551.2	549.0	542.6	542.1	528.0	525.3	516.2	512.1
7.5°	620.5	618.2	607.3	605.9	605.0	599.1	584.0	569.0	558.1	547.6	537.6
10°	690.2	683.4	678.4	668.3	663.3	655.1	635.5	621.4	602.7	586.8	565.8
12.5°	774.0	766.3	749.4	742.1	735.8	713.0	693.4	677.4	641.0	630.1	604.1
15°	835.5	819.1	817.3	801.4	800.4	775.4	738.0	720.7	692.5	652.4	625.5
17.5°	902.0	887.5	876.1	856.9	854.2	830.5	803.2	760.8	729.8	691.6	657.4
20°	950.8	943.0	923.5	915.7	899.8	879.7	851.5	799.1	761.3	723.0	681.1
22.5°	989.5	981.8	966.3	955.8	946.7	920.7	887.0	842.4	790.4	740.3	697.0
25°	989.1	986.8	980.4	975.4	968.6	949.4	921.2	878.3	820.5	765.4	705.2
27.5°	933.0	939.4	950.3	955.8	954.4	951.7	935.8	899.8	847.8	782.2	714.8
30°	816.4	839.6	860.1	887.5	895.7	915.7	924.8	904.3	862.9	801.8	727.1
32.5°	677.0	710.7	755.3	770.4	796.3	835.1	878.3	886.1	860.1	813.2	734.8
35°	555.3	583.1	617.8	641.5	664.7	727.6	782.2	829.6	838.3	807.3	733.0
37.5°	459.7	479.3	509.8	529.8	551.2	605.0	681.5	743.0	786.3	787.2	728.0
40°	390.4	399.1	425.5	440.1	460.6	507.1	575.4	655.6	718.9	748.1	714.8
42.5°	330.7	342.1	364.0	374.9	388.2	428.7	473.8	549.9	628.2	690.7	690.2
45°	295.2	303.4	313.4	322.5	337.6	361.7	413.2	470.2	545.3	615.9	643.7
47.5°	263.8	271.5	281.5	284.3	294.3	317.1	348.5	398.2	468.3	538.5	590.9
50°	237.4	243.7	250.6	255.6	260.1	278.8	302.5	344.4	400.5	468.3	533.5
52.5°	216.9	221.4	227.3	230.1	234.2	247.8	266.1	297.0	343.0	405.0	468.3
55°	197.7	200.9	204.6	209.1	210.9	221.0	235.1	261.5	295.7	351.2	411.4
57.5°	180.0	181.3	183.6	186.3	188.6	197.3	209.6	227.3	257.4	300.2	357.2
60°	159.9	163.6	164.9	167.7	169.0	175.9	185.4	200.5	223.7	260.6	303.4
62.5°	143.1	145.3	147.6	149.0	152.2	154.4	162.2	175.9	195.0	222.3	261.0
65°	128.0	128.9	130.3	131.7	132.6	135.3	142.6	151.7	166.3	190.4	220.5
67.5°	110.7	111.6	113.4	113.9	114.8	118.4	122.5	130.3	142.6	160.8	185.4
70°	93.8	95.2	96.1	97.0	98.4	99.8	104.3	110.7	120.3	133.0	152.2
72.5°	79.3	80.6	80.6	81.5	81.1	82.9	87.5	92.0	98.4	108.9	125.7
75°	64.7	64.7	65.6	66.1	66.5	68.3	70.2	73.8	78.8	87.0	97.5
77.5°	51.0	50.6	51.5	51.5	51.5	52.8	54.7	56.5	59.7	65.6	73.8
80°	37.4	37.4	38.3	38.7	37.8	38.3	39.2	41.0	43.3	47.4	51.9
82.5°	24.6	26.4	26.0	26.4	26.0	26.9	27.3	27.8	28.7	30.5	33.7
85°	15.0	15.0	15.0	15.5	15.0	15.5	15.5	15.5	15.9	16.9	18.2
87.5°	6.4	6.4	6.4	6.8	6.4	6.4	6.8	6.4	6.8	6.8	7.3
90°	28.8	27.8	28.8	27.8	26.8	25.8	24.8	23.8	24.8	21.8	18.9
92.5°	53.6	57.6	59.6	63.0	66.5	76.4	98.3	138.0	184.6	204.5	152.9
95°	126.1	135.0	153.8	171.7	189.6	242.2	357.3	477.4	588.6	524.1	361.3
97.5°	271.0	308.7	375.2	431.8	488.3	619.4	820.9	936.0	905.2	675.9	402.0
100°	660.1	732.5	832.8	903.2	973.7	1089.8	1170.2	1135.5	940.0	635.2	374.2
102.5°	1045.2	1098.8	1171.2	1209.4	1247.7	1303.2	1286.4	1145.4	875.4	575.7	350.4
105°	1299.3	1337.0	1382.6	1395.5	1408.4	1389.6	1290.3	1082.9	798.0	529.0	341.4
107.5°	1467.0	1484.9	1490.8	1477.4	1464.0	1386.6	1230.8	993.6	729.5	495.3	339.5
110°	1550.4	1542.4	1514.7	1480.0	1445.2	1320.1	1137.5	910.2	673.0	477.4	344.4



TEST NUMBER: P1011477

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1556.3	1527.6	1471.0	1423.8	1376.7	1232.8	1045.2	837.7	635.2	467.5	354.3
115°	1510.7	1467.0	1392.6	1338.5	1284.4	1138.5	965.8	782.1	610.4	466.5	365.3
117.5°	1429.3	1380.7	1303.2	1247.2	1191.1	1057.1	904.2	745.4	593.6	467.5	379.2
120°	1344.9	1289.3	1210.9	1160.8	1110.7	991.6	857.6	717.6	582.6	471.5	395.0
122.5°	1254.6	1206.0	1138.5	1092.8	1047.2	939.0	820.9	694.8	575.7	478.4	409.9
125°	1179.2	1135.5	1072.0	1032.3	992.6	897.3	789.1	675.9	569.7	485.4	425.8
127.5°	1114.6	1076.9	1019.4	982.6	945.9	858.6	760.3	658.1	566.8	493.3	438.7
130°	1059.1	1023.3	970.7	937.0	903.2	822.8	733.5	644.2	563.8	501.2	451.6
132.5°	1010.4	974.7	926.1	894.3	862.5	789.1	708.7	631.3	562.8	507.2	463.5
135°	956.8	927.1	878.4	850.1	821.8	757.3	686.9	620.4	561.8	513.2	473.5
137.5°	906.2	875.4	833.8	808.4	783.1	725.6	666.0	610.4	559.8	517.1	481.4
140°	854.6	826.8	789.1	767.8	746.4	698.8	648.1	601.5	558.8	521.1	487.3
142.5°	803.0	779.2	748.4	730.6	712.7	673.0	631.3	593.6	556.8	524.1	493.3
145°	757.3	736.5	711.7	697.3	682.9	651.1	618.4	586.6	554.8	525.1	497.3
147.5°	716.6	701.7	681.9	671.4	661.0	634.2	607.4	579.7	551.9	525.1	500.3
150°	683.9	673.0	658.1	648.7	639.2	618.4	595.5	572.7	547.9	525.1	501.2
152.5°	657.1	647.2	636.2	628.8	621.3	603.5	584.6	564.8	542.9	522.1	503.2
155°	633.3	625.3	616.4	610.4	604.5	589.6	573.7	556.8	537.0	520.1	503.2
157.5°	611.4	605.5	597.5	592.6	587.6	575.7	561.8	547.9	532.0	517.1	504.2
160°	592.6	586.6	579.7	576.2	572.7	562.8	551.9	539.0	526.1	515.1	504.2
162.5°	572.7	567.7	563.8	560.8	557.8	548.9	540.0	530.0	520.1	511.2	503.2
165°	555.8	551.9	547.9	545.4	542.9	536.0	530.0	522.1	514.1	507.2	501.2
167.5°	539.0	536.0	534.0	532.0	530.0	526.1	521.1	514.1	508.2	503.2	500.3
170°	524.1	522.1	521.1	520.1	519.1	515.1	512.2	507.2	502.2	499.3	497.3
172.5°	512.2	510.2	510.2	509.7	509.2	506.2	504.2	500.3	497.3	496.3	496.3
175°	501.2	500.3	500.3	500.3	500.3	498.3	497.3	495.3	493.3	493.3	494.3
177.5°	494.3	493.3	494.3	494.3	494.3	493.3	492.3	491.3	490.3	491.3	493.3
180°	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3

TEST NUMBER: P1011477

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	482.9	481.5	481.5	480.6	477.9	472.9	472.4	473.3	470.6	467.9	463.8
5°	506.6	497.9	495.2	492.5	487.0	477.9	474.3	471.1	466.1	460.1	453.8
7.5°	526.6	514.3	510.7	505.7	494.8	482.0	473.8	467.0	460.1	451.9	444.2
10°	551.7	533.9	525.3	518.0	503.0	485.2	472.9	462.9	451.9	441.9	431.9
12.5°	579.9	551.2	548.5	530.7	513.4	487.0	472.0	457.4	442.8	430.5	420.0
15°	603.6	572.2	560.8	549.0	515.7	482.9	468.3	451.9	435.1	421.9	406.4
17.5°	618.7	592.7	568.6	552.6	518.0	488.8	460.6	441.9	424.1	405.9	393.2
20°	636.9	599.1	578.1	556.7	522.5	484.3	456.0	432.8	410.9	394.5	379.0
22.5°	655.1	604.1	586.8	563.5	523.5	479.7	447.8	424.6	399.5	383.1	366.3
25°	653.3	611.4	582.7	563.1	514.3	475.6	438.3	410.9	387.7	366.7	349.9
27.5°	654.7	603.2	574.0	551.2	508.0	469.7	428.2	399.5	375.4	353.5	335.8
30°	655.1	590.9	565.4	538.0	496.1	455.6	416.9	387.7	362.2	338.5	322.5
32.5°	653.8	580.9	549.0	524.4	477.4	441.9	403.6	372.7	346.7	324.8	309.8
35°	650.6	569.0	532.1	501.1	458.3	422.3	391.3	359.4	331.7	311.6	294.3
37.5°	641.9	556.3	514.3	483.8	436.0	399.5	372.2	345.8	318.9	295.2	280.6
40°	635.5	538.9	496.6	463.3	411.8	376.3	353.5	328.5	302.0	280.6	266.5
42.5°	620.9	522.5	478.4	438.7	388.2	351.7	330.3	310.2	287.5	266.5	253.8
45°	597.3	504.8	456.0	415.9	362.2	327.6	308.0	291.6	271.5	251.5	238.7
47.5°	564.0	479.3	432.3	392.3	336.7	301.6	282.0	269.7	253.8	236.9	226.0
50°	528.0	451.5	408.2	368.6	312.1	277.9	258.8	247.4	236.9	221.4	210.9
52.5°	481.1	421.9	380.4	342.6	285.6	252.8	236.0	227.8	216.9	205.9	196.8
55°	435.5	383.6	349.4	313.4	259.7	229.2	212.8	204.1	197.7	188.6	181.3
57.5°	382.7	348.1	316.6	283.8	235.5	207.7	192.3	181.8	177.7	173.6	166.7
60°	333.9	307.5	282.0	254.7	210.5	185.4	170.4	162.2	158.1	155.4	150.8
62.5°	289.3	268.8	246.9	225.1	185.0	162.2	150.8	142.6	139.0	138.5	134.4
65°	246.5	231.9	214.1	192.7	161.3	141.2	130.3	125.3	121.2	121.2	118.0
67.5°	203.6	193.6	179.5	164.5	139.9	121.2	111.2	106.6	104.3	104.3	102.0
70°	169.5	162.6	149.9	136.7	115.3	101.1	93.4	89.3	87.9	88.4	86.6
72.5°	137.6	130.3	119.8	110.2	94.3	83.8	78.4	73.8	71.5	72.0	71.5
75°	106.6	103.0	93.8	86.6	73.8	66.5	61.5	59.2	57.4	57.9	56.9
77.5°	80.2	74.7	69.7	64.7	56.9	51.0	46.9	44.6	43.3	43.3	43.3
80°	54.7	53.8	49.7	46.9	40.5	36.0	32.8	32.3	31.0	31.0	31.0
82.5°	35.5	33.3	31.0	29.2	25.5	22.8	21.4	20.5	20.0	19.6	20.5
85°	19.6	18.2	17.3	15.5	14.1	12.8	11.4	10.9	10.5	10.9	10.5
87.5°	7.7	6.4	6.4	5.9	5.5	5.0	5.0	4.1	4.1	3.6	3.6
90°	15.9	12.9	11.9	10.9	8.9	6.0	4.0	2.0	4.0	6.0	8.9
92.5°	100.2	68.5	59.6	50.6	40.7	31.8	21.8	14.9	21.8	31.8	40.7
95°	213.4	129.0	109.6	90.3	64.5	47.6	36.7	33.7	36.7	47.6	64.5
97.5°	230.3	146.9	125.6	104.2	78.4	63.5	54.6	53.6	54.6	63.5	78.4
100°	227.3	157.8	138.4	119.1	95.3	81.4	74.4	73.4	74.4	81.4	95.3
102.5°	231.3	170.7	153.4	136.0	115.1	102.2	96.3	94.3	96.3	102.2	115.1
105°	239.2	185.6	170.2	154.8	136.0	124.1	118.1	115.1	118.1	124.1	136.0
107.5°	252.1	204.5	190.1	175.7	157.8	145.9	140.0	137.0	140.0	145.9	157.8
110°	269.0	224.3	210.4	196.5	179.7	168.7	163.8	160.8	163.8	168.7	179.7

TEST NUMBER: P1011477

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	285.9	245.2	231.8	218.4	201.5	190.6	185.6	182.6	185.6	190.6	201.5
115°	304.7	267.0	253.6	240.2	223.3	213.4	207.4	203.5	207.4	213.4	223.3
117.5°	324.6	286.9	274.4	262.0	243.2	234.2	229.3	224.3	229.3	234.2	243.2
120°	343.4	307.7	295.3	282.9	264.0	254.1	249.1	246.2	249.1	254.1	264.0
122.5°	363.3	328.5	315.1	301.7	283.9	273.0	268.0	265.0	268.0	273.0	283.9
125°	382.1	347.4	334.0	320.6	301.7	290.8	284.9	282.9	284.9	290.8	301.7
127.5°	399.0	365.3	351.9	338.5	317.6	306.7	299.8	296.8	299.8	306.7	317.6
130°	413.9	381.1	367.7	354.3	333.5	321.6	312.7	309.7	312.7	321.6	333.5
132.5°	426.8	395.0	382.1	369.2	348.4	333.5	323.6	319.6	323.6	333.5	348.4
135°	439.7	408.9	395.5	382.1	361.3	346.4	335.5	331.5	335.5	346.4	361.3
137.5°	448.6	418.9	406.4	394.0	373.2	357.3	346.4	342.4	346.4	357.3	373.2
140°	457.6	428.8	416.4	404.0	384.1	368.2	358.3	353.4	358.3	368.2	384.1
142.5°	464.5	436.7	425.3	413.9	394.0	380.2	369.2	365.3	369.2	380.2	394.0
145°	470.5	444.7	433.2	421.8	405.0	390.1	381.1	378.2	381.1	390.1	405.0
147.5°	475.4	451.6	441.7	431.8	414.9	402.0	393.1	391.1	393.1	402.0	414.9
150°	480.4	457.6	448.6	439.7	425.8	412.9	405.0	404.0	405.0	412.9	425.8
152.5°	483.4	464.5	456.0	447.6	435.7	424.8	416.9	416.9	416.9	424.8	435.7
155°	487.3	470.5	463.6	456.6	445.7	435.7	429.8	429.8	429.8	435.7	445.7
157.5°	489.3	475.4	470.0	464.5	454.6	445.7	440.7	439.7	440.7	445.7	454.6
160°	492.3	480.4	475.4	470.5	463.5	455.6	451.6	451.6	451.6	455.6	463.5
162.5°	493.3	483.4	479.4	475.4	469.5	463.5	460.5	460.5	460.5	463.5	469.5
165°	494.3	486.4	482.9	479.4	475.4	470.5	468.5	469.5	468.5	470.5	475.4
167.5°	494.3	488.3	485.8	483.4	480.4	476.4	475.4	476.4	475.4	476.4	480.4
170°	493.3	488.3	487.4	486.4	484.4	481.4	480.4	482.4	480.4	481.4	484.4
172.5°	493.3	489.3	488.8	488.3	487.3	485.4	485.4	486.4	485.4	485.4	487.3
175°	492.3	490.3	489.8	489.3	489.3	487.3	488.3	489.3	488.3	487.3	489.3
177.5°	491.3	490.3	490.3	490.3	490.3	489.3	490.3	491.3	490.3	489.3	490.3
180°	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3

TEST NUMBER: P1011477

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	462.9	462.4	463.3	460.6	456.0	453.8	447.4	446.0	445.6	446.0	446.5
5°	450.1	449.7	448.3	443.7	438.3	434.2	426.4	426.0	423.2	420.5	421.9
7.5°	437.8	436.0	433.3	427.3	420.0	415.5	409.1	404.6	400.9	398.6	396.8
10°	425.5	422.8	420.0	412.3	403.2	396.4	388.6	385.0	380.9	379.0	377.2
12.5°	409.6	406.8	401.8	392.7	387.2	378.6	370.8	367.2	364.9	361.3	359.0
15°	396.8	391.3	388.6	379.0	367.6	366.7	352.6	351.7	347.1	347.1	343.5
17.5°	382.2	378.1	373.1	363.5	355.3	347.1	339.9	337.1	333.0	332.1	330.3
20°	368.1	362.6	360.8	351.2	342.6	332.6	324.8	322.1	320.3	318.4	319.8
22.5°	353.5	349.0	344.4	335.8	329.4	319.4	314.8	312.1	309.3	308.4	308.9
25°	339.4	335.3	330.7	322.1	315.3	307.1	303.0	301.6	300.2	300.2	299.8
27.5°	325.7	321.6	317.5	309.8	303.0	297.0	293.8	292.5	291.1	292.0	292.9
30°	311.6	308.0	304.3	297.5	292.0	286.6	284.7	283.8	283.4	285.6	285.6
32.5°	298.9	295.7	292.9	286.6	281.1	276.5	275.2	275.6	276.1	277.4	278.4
35°	285.6	283.4	280.6	275.2	270.6	266.5	267.0	267.0	267.9	270.2	272.0
37.5°	273.8	270.6	268.3	263.8	260.1	256.5	257.9	259.2	260.1	262.9	263.8
40°	259.7	258.3	256.5	251.9	248.7	248.3	248.7	249.7	251.5	252.8	254.2
42.5°	248.3	246.5	244.2	240.5	237.8	238.3	238.7	239.6	240.5	242.8	244.2
45°	235.5	234.2	232.3	229.2	226.9	227.3	227.8	227.8	228.7	231.4	232.3
47.5°	221.4	221.9	219.6	216.4	215.0	215.0	215.0	215.9	218.2	219.1	219.6
50°	207.7	206.8	206.4	203.2	202.3	201.8	202.3	202.7	205.9	205.5	206.8
52.5°	193.2	193.2	192.7	190.9	189.5	189.5	188.6	190.9	191.8	192.7	194.1
55°	179.0	177.7	177.2	176.3	174.5	174.0	174.9	177.7	178.6	179.5	180.9
57.5°	163.6	163.6	162.6	161.3	161.3	161.3	161.3	163.1	164.5	165.4	168.1
60°	149.4	147.6	146.2	146.2	146.2	145.8	148.5	148.5	151.3	151.7	152.6
62.5°	132.6	131.7	130.8	131.2	130.8	131.7	132.6	134.4	134.9	136.2	137.6
65°	116.6	116.6	115.7	118.4	116.6	116.6	118.9	118.9	119.8	121.2	123.0
67.5°	101.1	101.6	100.7	100.7	101.6	102.0	102.5	104.3	104.8	106.6	108.9
70°	85.2	86.1	86.6	85.6	86.6	87.5	88.4	88.8	90.7	91.6	92.9
72.5°	71.1	72.0	70.6	71.1	71.5	72.4	72.9	73.8	74.7	77.4	78.4
75°	56.9	56.5	56.0	57.9	56.9	58.8	59.2	59.2	60.1	62.4	63.3
77.5°	43.7	43.7	44.2	43.3	44.6	44.2	44.6	46.0	47.4	47.4	51.0
80°	30.5	31.4	31.4	31.4	31.9	32.3	31.4	33.7	34.2	34.2	35.5
82.5°	19.6	20.0	19.6	20.5	20.5	21.4	21.0	21.4	22.3	23.2	23.7
85°	10.5	10.5	11.4	11.4	10.9	11.4	10.9	11.4	12.3	12.3	12.8
87.5°	3.6	3.6	3.6	3.6	4.1	3.6	4.1	4.1	3.6	3.6	5.0
90°	10.9	11.9	12.9	15.9	18.9	21.8	24.8	23.8	24.8	25.8	26.8
92.5°	50.6	59.6	68.5	100.2	152.9	204.5	184.6	138.0	98.3	76.4	66.5
95°	90.3	109.6	129.0	213.4	361.3	524.1	588.6	477.4	357.3	242.2	189.6
97.5°	104.2	125.6	146.9	230.3	402.0	675.9	905.2	936.0	820.9	619.4	488.3
100°	119.1	138.4	157.8	227.3	374.2	635.2	940.0	1135.5	1170.2	1089.8	973.7
102.5°	136.0	153.4	170.7	231.3	350.4	575.7	875.4	1145.4	1286.4	1303.2	1247.7
105°	154.8	170.2	185.6	239.2	341.4	529.0	798.0	1082.9	1290.3	1389.6	1408.4
107.5°	175.7	190.1	204.5	252.1	339.5	495.3	729.5	993.6	1230.8	1386.6	1464.0
110°	196.5	210.4	224.3	269.0	344.4	477.4	673.0	910.2	1137.5	1320.1	1445.2

TEST NUMBER: P1011477

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	218.4	231.8	245.2	285.9	354.3	467.5	635.2	837.7	1045.2	1232.8	1376.7
115°	240.2	253.6	267.0	304.7	365.3	466.5	610.4	782.1	965.8	1138.5	1284.4
117.5°	262.0	274.4	286.9	324.6	379.2	467.5	593.6	745.4	904.2	1057.1	1191.1
120°	282.9	295.3	307.7	343.4	395.0	471.5	582.6	717.6	857.6	991.6	1110.7
122.5°	301.7	315.1	328.5	363.3	409.9	478.4	575.7	694.8	820.9	939.0	1047.2
125°	320.6	334.0	347.4	382.1	425.8	485.4	569.7	675.9	789.1	897.3	992.6
127.5°	338.5	351.9	365.3	399.0	438.7	493.3	566.8	658.1	760.3	858.6	945.9
130°	354.3	367.7	381.1	413.9	451.6	501.2	563.8	644.2	733.5	822.8	903.2
132.5°	369.2	382.1	395.0	426.8	463.5	507.2	562.8	631.3	708.7	789.1	862.5
135°	382.1	395.5	408.9	439.7	473.5	513.2	561.8	620.4	686.9	757.3	821.8
137.5°	394.0	406.4	418.9	448.6	481.4	517.1	559.8	610.4	666.0	725.6	783.1
140°	404.0	416.4	428.8	457.6	487.3	521.1	558.8	601.5	648.1	698.8	746.4
142.5°	413.9	425.3	436.7	464.5	493.3	524.1	556.8	593.6	631.3	673.0	712.7
145°	421.8	433.2	444.7	470.5	497.3	525.1	554.8	586.6	618.4	651.1	682.9
147.5°	431.8	441.7	451.6	475.4	500.3	525.1	551.9	579.7	607.4	634.2	661.0
150°	439.7	448.6	457.6	480.4	501.2	525.1	547.9	572.7	595.5	618.4	639.2
152.5°	447.6	456.0	464.5	483.4	503.2	522.1	542.9	564.8	584.6	603.5	621.3
155°	456.6	463.6	470.5	487.3	503.2	520.1	537.0	556.8	573.7	589.6	604.5
157.5°	464.5	470.0	475.4	489.3	504.2	517.1	532.0	547.9	561.8	575.7	587.6
160°	470.5	475.4	480.4	492.3	504.2	515.1	526.1	539.0	551.9	562.8	572.7
162.5°	475.4	479.4	483.4	493.3	503.2	511.2	520.1	530.0	540.0	548.9	557.8
165°	479.4	482.9	486.4	494.3	501.2	507.2	514.1	522.1	530.0	536.0	542.9
167.5°	483.4	485.8	488.3	494.3	500.3	503.2	508.2	514.1	521.1	526.1	530.0
170°	486.4	487.4	488.3	493.3	497.3	499.3	502.2	507.2	512.2	515.1	519.1
172.5°	488.3	488.8	489.3	493.3	496.3	496.3	497.3	500.3	504.2	506.2	509.2
175°	489.3	489.8	490.3	492.3	494.3	493.3	493.3	495.3	497.3	498.3	500.3
177.5°	490.3	490.3	490.3	491.3	493.3	491.3	490.3	491.3	492.3	493.3	494.3
180°	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3

TEST NUMBER: P1011477

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	446.0	446.5	444.6	443.3	446.9	444.6	444.6	445.1	444.2	445.6	445.1
5°	421.0	421.4	418.2	419.1	417.3	416.9	416.4	419.1	418.7	418.2	419.1
7.5°	396.4	396.4	395.0	394.1	394.1	392.7	394.5	394.1	395.0	395.0	396.4
10°	375.8	376.8	374.5	372.2	371.7	372.2	372.2	372.7	373.1	376.3	375.8
12.5°	359.0	357.6	357.2	355.8	353.5	352.6	351.7	356.7	355.3	355.3	355.3
15°	340.3	343.5	343.0	338.9	338.0	339.9	338.9	338.9	343.5	343.0	342.6
17.5°	330.3	329.4	328.5	326.2	326.6	326.2	326.6	326.6	329.4	329.4	329.4
20°	318.9	317.1	317.1	316.2	316.2	314.8	316.6	317.1	318.9	318.9	319.4
22.5°	308.9	307.5	307.5	307.1	308.0	306.1	308.0	308.4	308.4	309.8	309.8
25°	300.2	299.3	299.3	300.2	300.2	300.2	300.2	302.0	300.7	301.1	300.7
27.5°	292.5	292.9	293.4	293.8	293.4	293.8	294.3	295.2	295.7	295.2	294.3
30°	285.2	286.6	287.0	287.0	287.9	288.4	288.8	288.8	289.3	287.9	288.8
32.5°	279.7	279.7	280.6	281.1	282.0	282.5	282.5	283.4	282.9	281.5	282.0
35°	272.0	272.0	273.8	274.7	276.1	275.6	276.1	276.1	276.5	275.6	274.3
37.5°	264.2	265.1	265.1	267.0	267.4	267.9	267.4	268.3	267.9	267.0	266.5
40°	255.1	254.7	255.1	256.5	256.9	256.9	256.9	257.9	257.9	257.9	257.4
42.5°	243.7	245.1	244.6	246.0	245.6	245.6	246.5	247.4	247.8	246.5	246.9
45°	232.8	232.8	233.7	233.7	234.2	234.2	236.0	235.1	236.0	235.1	235.5
47.5°	221.0	221.4	221.4	221.9	222.8	223.7	222.8	223.2	223.2	223.7	222.8
50°	207.7	207.7	208.7	210.0	211.8	210.9	210.5	212.3	210.9	210.9	210.0
52.5°	194.1	195.4	195.9	197.3	198.6	199.1	199.5	198.6	199.1	197.7	198.2
55°	180.9	181.3	183.1	184.5	185.9	185.9	185.4	185.9	186.3	184.5	184.5
57.5°	167.7	169.0	170.8	170.8	172.7	172.7	172.2	172.2	172.7	171.3	170.8
60°	153.5	154.9	157.2	157.2	159.9	160.4	159.5	158.5	158.5	157.2	157.6
62.5°	138.5	139.9	141.2	143.5	145.3	144.4	146.2	144.4	144.9	142.1	142.1
65°	125.3	125.7	128.0	130.3	130.3	131.2	130.3	130.8	129.4	129.4	127.6
67.5°	109.8	109.8	112.1	114.3	116.6	116.6	116.6	115.3	115.3	113.9	113.9
70°	96.1	95.7	97.9	99.3	100.7	101.1	100.2	99.8	98.9	97.5	97.0
72.5°	79.3	80.2	82.5	83.4	85.6	85.2	87.5	84.7	84.7	82.5	82.0
75°	64.2	65.1	67.4	68.8	70.2	70.2	71.5	70.2	68.3	67.4	67.0
77.5°	51.0	50.6	52.4	54.7	55.1	54.7	55.6	55.1	53.3	53.3	52.4
80°	36.4	37.8	39.6	39.2	41.0	40.5	40.5	39.6	39.6	38.3	39.2
82.5°	24.1	25.5	26.0	25.5	26.0	26.9	27.3	26.9	26.9	26.0	26.4
85°	12.8	12.8	13.7	14.1	13.7	13.7	14.1	15.5	14.6	13.7	14.6
87.5°	4.1	3.6	3.6	4.1	3.6	3.6	4.1	4.1	4.6	4.6	4.6
90°	27.8	28.8	27.8	28.8	29.8	28.8	29.8	28.8	27.8	28.8	27.8
92.5°	63.0	59.6	57.6	53.6	54.6	52.6	54.6	53.6	57.6	59.6	63.0
95°	171.7	153.8	135.0	126.1	119.1	115.1	119.1	126.1	135.0	153.8	171.7
97.5°	431.8	375.2	308.7	271.0	247.1	236.2	247.1	271.0	308.7	375.2	431.8
100°	903.2	832.8	732.5	660.1	621.3	622.3	621.3	660.1	732.5	832.8	903.2
102.5°	1209.4	1171.2	1098.8	1045.2	1014.4	985.6	1014.4	1045.2	1098.8	1171.2	1209.4
105°	1395.5	1382.6	1337.0	1299.3	1267.5	1262.5	1267.5	1299.3	1337.0	1382.6	1395.5
107.5°	1477.4	1490.8	1484.9	1467.0	1454.1	1443.2	1454.1	1467.0	1484.9	1490.8	1477.4
110°	1480.0	1514.7	1542.4	1550.4	1548.4	1546.4	1548.4	1550.4	1542.4	1514.7	1480.0

TEST NUMBER: P1011477

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1423.8	1471.0	1527.6	1556.3	1566.3	1567.3	1566.3	1556.3	1527.6	1471.0	1423.8
115°	1338.5	1392.6	1467.0	1510.7	1530.5	1535.5	1530.5	1510.7	1467.0	1392.6	1338.5
117.5°	1247.2	1303.2	1380.7	1429.3	1459.1	1466.0	1459.1	1429.3	1380.7	1303.2	1247.2
120°	1160.8	1210.9	1289.3	1344.9	1368.7	1374.7	1368.7	1344.9	1289.3	1210.9	1160.8
122.5°	1092.8	1138.5	1206.0	1254.6	1281.4	1289.3	1281.4	1254.6	1206.0	1138.5	1092.8
125°	1032.3	1072.0	1135.5	1179.2	1204.0	1210.9	1204.0	1179.2	1135.5	1072.0	1032.3
127.5°	982.6	1019.4	1076.9	1114.6	1137.5	1143.4	1137.5	1114.6	1076.9	1019.4	982.6
130°	937.0	970.7	1023.3	1059.1	1079.9	1087.8	1079.9	1059.1	1023.3	970.7	937.0
132.5°	894.3	926.1	974.7	1010.4	1028.3	1033.3	1028.3	1010.4	974.7	926.1	894.3
135°	850.1	878.4	927.1	956.8	974.7	981.6	974.7	956.8	927.1	878.4	850.1
137.5°	808.4	833.8	875.4	906.2	921.1	927.1	921.1	906.2	875.4	833.8	808.4
140°	767.8	789.1	826.8	854.6	870.5	869.5	870.5	854.6	826.8	789.1	767.8
142.5°	730.6	748.4	779.2	803.0	816.9	815.9	816.9	803.0	779.2	748.4	730.6
145°	697.3	711.7	736.5	757.3	765.3	767.3	765.3	757.3	736.5	711.7	697.3
147.5°	671.4	681.9	701.7	716.6	724.6	725.6	724.6	716.6	701.7	681.9	671.4
150°	648.7	658.1	673.0	683.9	689.8	689.8	689.8	683.9	673.0	658.1	648.7
152.5°	628.8	636.2	647.2	657.1	660.1	660.1	660.1	657.1	647.2	636.2	628.8
155°	610.4	616.4	625.3	633.3	635.2	636.2	635.2	633.3	625.3	616.4	610.4
157.5°	592.6	597.5	605.5	611.4	613.4	613.4	613.4	611.4	605.5	597.5	592.6
160°	576.2	579.7	586.6	592.6	592.6	591.6	592.6	592.6	586.6	579.7	576.2
162.5°	560.8	563.8	567.7	572.7	572.7	571.7	572.7	572.7	567.7	563.8	560.8
165°	545.4	547.9	551.9	555.8	554.8	554.8	554.8	555.8	551.9	547.9	545.4
167.5°	532.0	534.0	536.0	539.0	538.0	538.0	538.0	539.0	536.0	534.0	532.0
170°	520.1	521.1	522.1	524.1	523.1	523.1	523.1	524.1	522.1	521.1	520.1
172.5°	509.7	510.2	510.2	512.2	510.2	509.2	510.2	512.2	510.2	510.2	509.7
175°	500.3	500.3	500.3	501.2	500.3	499.3	500.3	501.2	500.3	500.3	500.3
177.5°	494.3	494.3	493.3	494.3	492.3	492.3	492.3	494.3	493.3	494.3	494.3
180°	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3

TEST NUMBER: P1011477

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	446.5	447.4	447.8	446.0	444.6	446.9	450.1	452.4	454.2	456.5	457.9
5°	420.0	423.2	423.2	424.1	425.5	427.8	433.7	437.8	441.5	444.2	446.5
7.5°	397.7	400.0	401.4	403.6	405.9	409.1	415.9	421.9	427.3	430.5	434.2
10°	377.7	379.5	381.8	383.1	387.2	391.8	400.5	405.5	411.8	416.9	421.4
12.5°	358.5	364.9	366.3	365.8	369.5	374.5	383.1	390.9	397.7	402.7	407.7
15°	344.9	347.1	349.9	349.4	357.2	358.5	365.8	374.9	384.1	387.2	391.8
17.5°	329.8	333.5	336.2	337.6	339.9	344.9	351.7	358.5	370.4	370.8	382.7
20°	318.0	321.6	323.5	325.3	326.6	332.6	338.5	346.2	355.8	360.8	367.2
22.5°	310.2	312.1	313.4	314.8	316.6	319.8	327.1	335.8	342.1	347.6	351.7
25°	301.1	303.0	304.8	305.7	307.1	308.9	314.3	321.2	330.3	333.9	338.0
27.5°	294.8	294.8	295.7	295.7	297.5	299.3	303.4	309.8	317.1	321.6	327.1
30°	287.9	287.5	287.9	287.5	287.0	289.7	293.4	298.9	303.9	309.3	313.0
32.5°	281.1	280.6	280.6	281.1	279.3	280.6	282.5	287.5	292.9	295.7	299.8
35°	273.8	272.9	272.9	272.9	272.0	271.1	272.9	277.4	281.1	284.7	287.9
37.5°	266.5	265.1	265.1	264.2	263.3	262.0	262.0	265.6	270.6	272.0	276.1
40°	256.5	256.5	255.6	255.1	254.2	253.3	251.9	255.1	259.7	261.0	264.2
42.5°	246.5	245.1	244.6	244.6	244.6	243.3	242.4	244.6	247.4	249.7	251.5
45°	235.1	234.2	234.6	234.2	233.3	232.8	232.3	233.3	236.4	237.4	239.6
47.5°	222.8	222.3	222.3	221.9	221.4	221.9	220.0	222.3	223.2	224.1	226.0
50°	210.0	209.6	209.1	208.7	208.7	209.1	208.7	208.7	210.5	211.4	213.2
52.5°	197.3	195.9	195.9	195.4	195.4	194.5	195.4	195.9	196.8	197.7	198.6
55°	183.6	183.6	182.2	182.2	181.3	181.3	181.8	181.3	183.1	184.1	184.1
57.5°	170.4	168.6	169.0	168.1	167.2	166.7	166.7	167.7	168.6	168.6	169.5
60°	156.3	154.4	154.0	152.2	153.1	151.7	152.2	152.2	154.0	153.1	154.0
62.5°	142.1	139.9	138.5	137.6	137.6	138.0	137.1	136.7	137.6	138.5	140.3
65°	127.1	125.7	124.4	123.0	123.0	122.5	123.5	122.1	121.6	122.1	123.0
67.5°	111.6	110.2	108.9	107.5	108.0	106.6	105.7	107.1	106.1	106.6	107.5
70°	96.6	95.7	92.9	92.0	91.6	92.0	91.6	90.7	92.0	91.6	92.0
72.5°	81.5	80.6	79.3	77.0	77.0	76.5	76.1	76.1	75.6	75.6	75.6
75°	67.0	65.1	63.8	63.3	62.4	62.0	61.5	60.6	61.0	61.5	60.6
77.5°	51.9	49.7	49.2	49.2	47.8	47.8	48.3	47.8	47.4	47.4	47.4
80°	38.3	36.4	36.4	35.5	34.6	34.6	34.6	34.6	34.2	33.7	34.2
82.5°	24.6	24.1	23.7	23.7	24.6	22.8	23.7	23.2	22.8	22.8	22.3
85°	13.7	14.1	13.7	14.1	13.2	13.7	13.7	13.7	13.2	13.7	12.8
87.5°	5.0	5.0	5.0	5.5	5.5	5.5	5.5	5.5	5.9	5.5	5.5
90°	26.8	25.8	24.8	23.8	24.8	21.8	18.9	15.9	12.9	11.9	10.9
92.5°	66.5	76.4	98.3	138.0	184.6	204.5	152.9	100.2	68.5	59.6	50.6
95°	189.6	242.2	357.3	477.4	588.6	524.1	361.3	213.4	129.0	109.6	90.3
97.5°	488.3	619.4	820.9	936.0	905.2	675.9	402.0	230.3	146.9	125.6	104.2
100°	973.7	1089.8	1170.2	1135.5	940.0	635.2	374.2	227.3	157.8	138.4	119.1
102.5°	1247.7	1303.2	1286.4	1145.4	875.4	575.7	350.4	231.3	170.7	153.4	136.0
105°	1408.4	1389.6	1290.3	1082.9	798.0	529.0	341.4	239.2	185.6	170.2	154.8
107.5°	1464.0	1386.6	1230.8	993.6	729.5	495.3	339.5	252.1	204.5	190.1	175.7
110°	1445.2	1320.1	1137.5	910.2	673.0	477.4	344.4	269.0	224.3	210.4	196.5

TEST NUMBER: P1011477

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1376.7	1232.8	1045.2	837.7	635.2	467.5	354.3	285.9	245.2	231.8	218.4
115°	1284.4	1138.5	965.8	782.1	610.4	466.5	365.3	304.7	267.0	253.6	240.2
117.5°	1191.1	1057.1	904.2	745.4	593.6	467.5	379.2	324.6	286.9	274.4	262.0
120°	1110.7	991.6	857.6	717.6	582.6	471.5	395.0	343.4	307.7	295.3	282.9
122.5°	1047.2	939.0	820.9	694.8	575.7	478.4	409.9	363.3	328.5	315.1	301.7
125°	992.6	897.3	789.1	675.9	569.7	485.4	425.8	382.1	347.4	334.0	320.6
127.5°	945.9	858.6	760.3	658.1	566.8	493.3	438.7	399.0	365.3	351.9	338.5
130°	903.2	822.8	733.5	644.2	563.8	501.2	451.6	413.9	381.1	367.7	354.3
132.5°	862.5	789.1	708.7	631.3	562.8	507.2	463.5	426.8	395.0	382.1	369.2
135°	821.8	757.3	686.9	620.4	561.8	513.2	473.5	439.7	408.9	395.5	382.1
137.5°	783.1	725.6	666.0	610.4	559.8	517.1	481.4	448.6	418.9	406.4	394.0
140°	746.4	698.8	648.1	601.5	558.8	521.1	487.3	457.6	428.8	416.4	404.0
142.5°	712.7	673.0	631.3	593.6	556.8	524.1	493.3	464.5	436.7	425.3	413.9
145°	682.9	651.1	618.4	586.6	554.8	525.1	497.3	470.5	444.7	433.2	421.8
147.5°	661.0	634.2	607.4	579.7	551.9	525.1	500.3	475.4	451.6	441.7	431.8
150°	639.2	618.4	595.5	572.7	547.9	525.1	501.2	480.4	457.6	448.6	439.7
152.5°	621.3	603.5	584.6	564.8	542.9	522.1	503.2	483.4	464.5	456.0	447.6
155°	604.5	589.6	573.7	556.8	537.0	520.1	503.2	487.3	470.5	463.6	456.6
157.5°	587.6	575.7	561.8	547.9	532.0	517.1	504.2	489.3	475.4	470.0	464.5
160°	572.7	562.8	551.9	539.0	526.1	515.1	504.2	492.3	480.4	475.4	470.5
162.5°	557.8	548.9	540.0	530.0	520.1	511.2	503.2	493.3	483.4	479.4	475.4
165°	542.9	536.0	530.0	522.1	514.1	507.2	501.2	494.3	486.4	482.9	479.4
167.5°	530.0	526.1	521.1	514.1	508.2	503.2	500.3	494.3	488.3	485.8	483.4
170°	519.1	515.1	512.2	507.2	502.2	499.3	497.3	493.3	488.3	487.4	486.4
172.5°	509.2	506.2	504.2	500.3	497.3	496.3	496.3	493.3	489.3	488.8	488.3
175°	500.3	498.3	497.3	495.3	493.3	493.3	494.3	492.3	490.3	489.8	489.3
177.5°	494.3	493.3	492.3	491.3	490.3	491.3	493.3	491.3	490.3	490.3	490.3
180°	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3

TEST NUMBER: P1011477

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	470.2	470.2	470.2	470.2
2.5°	460.1	461.5	466.1	471.5
5°	451.0	454.7	461.0	469.7
7.5°	441.0	446.5	455.6	466.5
10°	429.6	437.4	448.7	462.4
12.5°	417.3	427.3	441.9	456.0
15°	409.6	419.6	432.8	448.3
17.5°	394.5	406.4	420.0	441.9
20°	379.0	392.3	410.0	431.9
22.5°	367.2	381.3	398.2	421.4
25°	353.1	367.6	385.9	410.0
27.5°	338.0	352.6	373.1	398.6
30°	326.6	340.8	360.4	387.7
32.5°	313.0	326.6	347.1	375.8
35°	297.5	313.0	332.6	361.7
37.5°	285.6	299.8	320.3	348.1
40°	272.9	285.2	305.2	332.6
42.5°	259.2	272.9	290.2	317.5
45°	246.5	256.5	274.3	300.2
47.5°	232.8	244.2	257.9	277.9
50°	218.2	227.8	242.8	256.5
52.5°	204.1	211.8	224.6	235.1
55°	189.1	196.8	206.4	212.8
57.5°	174.9	180.4	186.8	190.9
60°	157.6	163.1	167.2	171.3
62.5°	142.1	146.2	148.5	150.8
65°	126.2	128.5	129.8	131.7
67.5°	108.9	111.2	111.6	114.3
70°	92.9	93.4	94.3	95.7
72.5°	77.9	78.8	78.4	79.3
75°	62.4	63.3	62.4	63.3
77.5°	47.4	48.3	48.3	49.7
80°	34.2	34.6	35.1	35.1
82.5°	22.3	23.7	22.8	23.2
85°	12.8	13.2	13.2	13.7
87.5°	5.9	6.4	5.9	6.8
90°	8.9	6.0	4.0	2.0
92.5°	40.7	31.8	21.8	14.9
95°	64.5	47.6	36.7	33.7
97.5°	78.4	63.5	54.6	53.6
100°	95.3	81.4	74.4	73.4
102.5°	115.1	102.2	96.3	94.3
105°	136.0	124.1	118.1	115.1
107.5°	157.8	145.9	140.0	137.0
110°	179.7	168.7	163.8	160.8

TEST NUMBER: P1011477

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	201.5	190.6	185.6	182.6
115°	223.3	213.4	207.4	203.5
117.5°	243.2	234.2	229.3	224.3
120°	264.0	254.1	249.1	246.2
122.5°	283.9	273.0	268.0	265.0
125°	301.7	290.8	284.9	282.9
127.5°	317.6	306.7	299.8	296.8
130°	333.5	321.6	312.7	309.7
132.5°	348.4	333.5	323.6	319.6
135°	361.3	346.4	335.5	331.5
137.5°	373.2	357.3	346.4	342.4
140°	384.1	368.2	358.3	353.4
142.5°	394.0	380.2	369.2	365.3
145°	405.0	390.1	381.1	378.2
147.5°	414.9	402.0	393.1	391.1
150°	425.8	412.9	405.0	404.0
152.5°	435.7	424.8	416.9	416.9
155°	445.7	435.7	429.8	429.8
157.5°	454.6	445.7	440.7	439.7
160°	463.5	455.6	451.6	451.6
162.5°	469.5	463.5	460.5	460.5
165°	475.4	470.5	468.5	469.5
167.5°	480.4	476.4	475.4	476.4
170°	484.4	481.4	480.4	482.4
172.5°	487.3	485.4	485.4	486.4
175°	489.3	487.3	488.3	489.3
177.5°	490.3	489.3	490.3	491.3
180°	490.3	490.3	490.3	490.3

(END OF REPORT)