

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011513

Luminaire Tested: S123DIP-B340D1195UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011513
REPORT IS A COMBINATION OF REPORTS P989705 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D1195UB30-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5731.0 lumens
Efficiency: N/A
Efficacy: 119.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011513

CATALOG NUMBER: S123DIP-B340D1195UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1011513

CATALOG NUMBER: S123DIP-B340D1195UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33
1	92	88	84	81	82	79	76	73	61	59	57	44	43	42	29	29	28
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	23	22	20
4	70	60	52	47	62	54	47	42	42	37	34	31	28	26	21	19	18
5	64	53	46	40	57	48	41	36	37	33	29	28	25	22	19	17	15
6	59	48	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13
7	54	43	35	30	48	38	32	27	30	26	22	23	19	17	15	13	12
8	50	39	31	26	45	35	28	24	27	23	19	21	17	15	14	12	11
9	47	35	28	23	42	32	25	21	25	21	17	19	16	13	13	11	10
10	44	32	25	21	39	29	23	19	23	19	15	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5040	5040	5040	5040
5°	5042	5807	5058	4334
10°	5011	7026	5016	3784
15°	4941	8333	4981	3406
20°	4882	9594	4892	3135
25°	4793	9835	4804	2993
30°	4731	8126	4731	2900
35°	4652	5434	4622	2818
40°	4558	3923	4502	2692
45°	4441	3108	4311	2536
50°	4153	2639	4005	2381
55°	3839	2319	3682	2211
60°	3520	2019	3332	2031
65°	3169	1729	3017	1792
70°	2806	1435	2618	1510
75°	2400	1083	2244	1166
80°	1895	723	1748	766
85°	1306	332	1047	301

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 8127 cd/sqm

TEST NUMBER: P1011513

CATALOG NUMBER: S123DIP-B340D1195UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.0	0.8
10°-20°	147.9	2.6
20°-30°	248.8	4.3
30°-40°	281.2	4.9
40°-50°	251.9	4.4
50°-60°	203.3	3.5
60°-70°	141.7	2.5
70°-80°	74.4	1.3
80°-90°	21.0	0.4
90°-100°	311.3	5.4
100°-110°	911.3	15.9
110°-120°	889.9	15.5
120°-130°	708.7	12.4
130°-140°	559.2	9.8
140°-150°	417.1	7.3
150°-160°	290.9	5.1
160°-170°	170.9	3.0
170°-180°	55.6	1.0
0°-30°	442.8	7.7
0°-40°	724.0	12.6
0°-60°	1179.1	20.6
0°-90°	1416.2	24.7
90°-120°	2112.5	36.9
90°-150°	3797.6	66.3
90°-180°	4315.0	75.3
0°-180°	5731.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	468	468	468	468	468	
5°	468	556	469	415	468	44
15°	446	828	450	338	446	126
25°	408	983	409	299	408	188
35°	360	529	358	274	360	225
45°	299	286	290	233	299	229
55°	212	194	203	185	212	190
65°	131	126	125	131	131	131
75°	63	65	59	70	63	68
85°	14	15	11	14	14	16
90°	2	34	2	34	2	4
95°	40	135	40	135	40	42
105°	135	1477	135	1477	135	143
115°	238	1796	238	1796	238	236
125°	331	1417	331	1417	331	294
135°	388	1148	388	1148	388	300
145°	442	898	442	898	442	277
155°	503	744	503	744	503	231
165°	549	649	549	649	549	155
175°	572	584	572	584	572	54
180°	574	574	574	574	574	

TEST NUMBER: P1011513

CATALOG NUMBER: S123DIP-B340D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2
2.5°	469.5	473.2	475.0	477.7	480.4	484.5	485.9	488.1	487.2	489.0	489.9
5°	467.7	474.1	479.5	486.3	492.7	497.2	501.7	509.0	514.4	515.3	519.4
7.5°	464.5	473.6	483.1	492.7	504.9	512.2	520.3	530.3	538.5	551.6	556.6
10°	460.5	473.2	486.8	499.9	516.7	528.0	538.0	554.8	571.6	585.2	597.9
12.5°	454.1	470.0	487.7	507.2	529.0	542.1	555.7	577.9	603.4	624.2	637.8
15°	446.4	466.4	489.0	509.9	533.9	558.4	573.0	597.9	634.2	653.7	688.6
17.5°	440.0	460.5	483.1	515.8	548.5	573.0	583.4	629.2	654.2	686.8	726.3
20°	430.1	455.9	485.0	517.6	559.8	574.8	596.1	642.4	673.2	715.9	764.4
22.5°	419.6	447.3	482.2	516.3	563.4	579.3	608.3	645.1	694.1	736.3	789.8
25°	408.3	438.2	473.6	514.0	560.3	583.4	610.6	656.0	709.1	762.1	811.6
27.5°	396.9	429.6	466.4	506.7	551.6	578.9	606.1	653.3	721.3	778.9	842.0
30°	386.1	418.7	455.5	496.7	543.9	570.2	596.1	655.1	730.8	795.7	859.2
32.5°	374.3	407.8	446.4	480.9	528.5	556.6	585.7	655.1	736.7	805.7	863.7
35°	360.2	394.7	427.8	462.3	509.4	540.7	573.4	650.5	742.2	808.9	844.7
37.5°	346.6	377.0	405.6	439.1	488.6	522.2	559.8	645.1	739.4	795.2	805.2
40°	331.2	361.6	384.7	416.0	468.2	507.2	545.3	637.8	727.7	763.0	734.0
42.5°	316.2	340.2	360.2	390.6	447.3	485.4	526.7	624.7	704.5	711.8	646.5
45°	299.0	316.2	333.9	368.4	424.6	463.6	509.4	605.6	667.3	646.5	563.9
47.5°	276.7	292.2	311.7	343.4	400.6	440.9	484.5	581.1	613.3	569.8	479.5
50°	255.4	268.6	286.7	317.6	375.2	414.6	460.9	542.6	558.4	489.9	413.3
52.5°	234.1	244.1	261.8	292.6	350.2	388.3	430.5	503.1	494.0	420.5	352.5
55°	211.9	220.5	237.3	267.7	321.2	357.5	397.9	454.6	431.0	361.1	306.7
57.5°	190.1	199.2	216.4	241.8	292.2	327.5	359.7	404.2	368.8	313.0	264.9
60°	170.6	178.3	191.4	216.4	262.2	290.8	320.3	350.7	321.2	267.2	230.5
62.5°	150.2	157.4	169.7	192.3	231.8	257.2	280.8	305.8	273.1	233.6	201.0
65°	131.1	137.0	148.3	169.2	201.4	222.3	241.3	258.6	232.3	196.0	171.5
67.5°	113.9	118.9	128.4	147.0	174.2	189.2	204.6	219.1	196.9	167.9	147.0
70°	95.3	99.3	108.0	121.6	143.4	158.8	170.1	181.0	161.0	137.9	123.8
72.5°	78.9	83.0	88.5	102.5	117.5	127.0	139.3	145.2	133.8	114.8	100.7
75°	63.1	66.2	71.2	80.3	94.4	100.7	108.4	113.0	102.5	89.8	81.2
77.5°	49.4	50.8	54.4	60.8	70.3	77.6	83.5	86.2	78.9	70.8	63.5
80°	34.9	36.7	39.5	44.9	52.2	54.4	58.1	61.2	56.7	49.4	44.9
82.5°	23.1	25.4	26.8	29.0	33.6	36.3	37.2	39.9	35.8	33.1	31.3
85°	13.6	14.5	15.0	16.3	18.6	20.0	21.3	21.8	20.9	20.4	18.6
87.5°	6.8	6.8	6.8	7.7	8.2	9.1	9.5	9.5	9.5	9.1	8.6
90°	2.3	4.6	7.0	10.5	12.8	14.0	15.1	18.6	22.1	25.5	29.0
92.5°	17.4	25.5	37.2	47.6	59.2	69.6	80.1	117.3	178.8	239.2	216.0
95°	39.5	43.0	55.7	75.5	105.7	128.4	151.0	249.7	422.7	613.1	688.6
97.5°	62.7	63.9	74.3	91.7	121.9	146.9	171.9	269.4	470.3	790.8	1059.0
100°	85.9	87.1	95.2	111.5	139.3	162.0	184.6	265.9	437.8	743.2	1099.6
102.5°	110.3	112.6	119.6	134.7	159.1	179.4	199.7	270.6	409.9	673.5	1024.2
105°	134.7	138.2	145.1	159.1	181.1	199.1	217.1	279.8	399.4	618.9	933.6
107.5°	160.2	163.7	170.7	184.6	205.5	222.4	239.2	294.9	397.1	579.4	853.5
110°	188.1	191.6	197.4	210.2	229.9	246.2	262.4	314.7	402.9	558.5	787.3

TEST NUMBER: P1011513

CATALOG NUMBER: S123DIP-B340D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	213.7	217.1	222.9	235.7	255.5	271.2	286.8	334.4	414.5	546.9	743.2
115°	238.0	242.7	249.7	261.3	281.0	296.7	312.4	356.5	427.3	545.8	714.1
117.5°	262.4	268.2	274.0	284.5	306.5	321.0	335.6	379.7	443.6	546.9	694.4
120°	288.0	291.5	297.3	308.9	330.9	345.4	360.0	401.8	462.1	551.6	681.6
122.5°	310.0	313.5	319.3	332.1	353.0	368.6	384.3	425.0	479.6	559.7	673.5
125°	330.9	333.3	340.2	353.0	375.1	390.8	406.4	447.1	498.1	567.8	666.5
127.5°	347.2	350.7	358.8	371.6	396.0	411.6	427.3	466.8	513.2	577.1	663.0
130°	362.3	365.8	376.2	390.2	414.5	430.2	445.9	484.2	528.3	586.4	659.5
132.5°	373.9	378.5	390.2	407.6	432.0	447.0	462.1	499.3	542.3	593.4	658.4
135°	387.8	392.5	405.2	422.7	447.1	462.8	478.4	514.4	553.9	600.3	657.2
137.5°	400.6	405.2	418.0	436.6	461.0	475.5	490.0	524.9	563.2	605.0	654.9
140°	413.4	419.2	430.8	449.4	472.6	487.1	501.6	535.3	570.1	609.6	653.7
142.5°	427.3	432.0	444.7	461.0	484.2	497.6	510.9	543.4	577.1	613.1	651.4
145°	442.4	445.9	456.3	473.8	493.5	506.8	520.2	550.4	581.7	614.3	649.1
147.5°	457.5	459.8	470.3	485.4	505.1	516.7	528.3	556.2	585.2	614.3	645.6
150°	472.6	473.8	483.0	498.1	514.4	524.8	535.3	562.0	586.4	614.3	641.0
152.5°	487.7	487.7	497.0	509.8	523.7	533.6	543.4	565.5	588.7	610.8	635.2
155°	502.8	502.8	509.8	521.4	534.1	542.2	550.4	570.1	588.7	608.5	628.2
157.5°	514.4	515.6	521.4	531.8	543.4	549.8	556.2	572.5	589.9	605.0	622.4
160°	528.3	528.3	533.0	542.3	550.4	556.2	562.0	575.9	589.9	602.6	615.4
162.5°	538.8	538.8	542.3	549.2	556.2	560.8	565.5	577.1	588.7	598.0	608.5
165°	549.2	548.1	550.4	556.2	560.8	564.9	569.0	578.3	586.4	593.4	601.5
167.5°	557.4	556.2	557.4	562.0	565.5	568.4	571.3	578.3	585.2	588.7	594.5
170°	564.3	562.0	563.2	566.7	569.0	570.2	571.3	577.1	581.7	584.1	587.6
172.5°	569.0	567.8	567.8	570.1	571.3	571.9	572.5	577.1	580.6	580.6	581.7
175°	572.5	571.3	570.1	572.5	572.5	573.0	573.6	575.9	578.3	577.1	577.1
177.5°	574.8	573.6	572.5	573.6	573.6	573.6	573.6	574.8	577.1	574.8	573.6
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1011513

CATALOG NUMBER: S123DIP-B340D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2
2.5°	493.1	494.0	497.2	499.5	504.0	503.6	503.6	503.1	501.7	504.0	505.4
5°	527.6	535.3	536.2	546.2	546.6	550.7	553.5	551.2	556.6	556.2	552.1
7.5°	570.2	580.7	585.7	595.2	606.1	603.4	613.8	615.6	614.7	619.2	622.4
10°	617.0	635.1	647.8	665.5	670.0	672.8	679.6	685.5	697.3	688.2	694.1
12.5°	670.5	683.6	700.4	728.6	742.6	751.7	754.9	759.0	767.1	762.1	762.6
15°	715.4	733.1	761.7	796.6	800.7	812.0	809.3	833.8	845.6	827.9	837.9
17.5°	762.1	785.7	819.7	850.1	867.4	875.1	882.3	905.9	905.0	902.3	904.6
20°	792.1	830.6	872.8	913.2	918.2	924.1	943.6	953.6	951.8	959.5	964.5
22.5°	834.3	875.1	920.0	946.8	958.1	964.9	980.3	986.7	989.4	991.2	988.0
25°	869.6	913.2	946.3	969.9	976.7	980.3	985.3	987.1	985.8	982.6	985.3
27.5°	893.7	928.6	951.3	962.2	958.6	952.7	943.1	936.8	922.7	915.9	924.1
30°	903.7	919.1	925.9	907.8	889.6	875.1	856.9	823.4	797.1	804.8	794.3
32.5°	887.8	877.8	845.1	798.4	784.4	760.8	709.5	670.0	671.4	650.5	659.2
35°	841.1	795.7	734.0	663.2	644.6	631.9	575.7	567.1	548.9	529.4	534.9
37.5°	758.5	692.3	617.4	565.2	537.6	509.9	478.1	459.1	448.2	440.0	446.4
40°	657.8	577.0	515.3	468.6	445.0	427.3	405.6	386.5	374.3	372.9	375.2
42.5°	558.9	490.8	434.1	389.7	382.0	361.1	347.0	332.1	328.4	322.5	325.7
45°	473.2	417.8	371.1	334.8	325.7	320.3	303.0	293.5	289.4	285.8	291.2
47.5°	411.0	352.9	318.9	297.1	288.1	279.0	269.5	263.1	259.9	260.4	259.9
50°	351.1	308.5	278.5	261.8	256.3	250.0	242.2	238.2	236.8	232.7	235.9
52.5°	302.1	271.3	250.4	234.5	230.5	225.9	219.6	217.3	214.1	213.2	213.2
55°	262.7	238.6	221.8	211.4	206.4	202.8	199.2	196.4	194.2	194.2	194.2
57.5°	231.8	210.9	198.7	189.6	187.8	184.2	180.1	180.1	176.9	176.5	177.8
60°	205.5	186.9	177.4	169.7	166.9	166.0	162.0	162.0	161.0	158.8	160.6
62.5°	178.7	165.1	157.0	151.1	148.3	148.3	145.2	142.9	142.9	143.4	142.4
65°	154.2	144.3	137.0	132.5	131.1	129.3	128.8	127.0	125.7	126.1	125.7
67.5°	132.5	124.8	119.8	116.1	113.9	113.0	111.6	111.6	110.7	111.1	108.9
70°	113.0	105.2	101.2	97.5	96.6	96.6	94.8	95.3	94.4	95.7	94.8
72.5°	93.0	87.1	83.9	82.6	81.7	81.2	80.3	79.4	78.9	79.8	79.4
75°	75.3	70.3	68.0	67.1	66.2	66.2	65.8	65.3	64.9	64.9	64.9
77.5°	58.5	55.3	52.6	53.5	52.2	52.6	51.3	51.3	51.7	51.3	51.3
80°	43.1	40.8	40.8	39.9	38.1	39.0	39.0	37.7	37.2	38.1	36.7
82.5°	28.6	28.1	27.2	26.8	25.9	26.3	25.9	25.4	25.0	25.9	25.0
85°	16.8	16.8	16.3	15.4	16.3	15.9	15.4	15.4	15.0	15.0	15.0
87.5°	8.6	7.7	7.7	7.3	7.7	6.8	7.3	6.8	6.4	6.8	6.4
90°	27.9	29.0	30.2	31.4	32.6	33.7	32.5	33.7	34.8	33.7	34.8
92.5°	161.4	115.0	89.4	77.8	73.8	69.7	67.3	62.7	63.9	61.5	63.9
95°	558.5	418.0	283.3	221.8	200.9	180.0	157.9	147.5	139.3	134.7	139.3
97.5°	1095.0	960.3	724.6	571.3	505.1	438.9	361.1	317.0	289.1	276.4	289.1
100°	1328.4	1369.0	1275.0	1139.1	1056.6	974.2	856.9	772.2	726.9	728.1	726.9
102.5°	1340.0	1504.9	1524.6	1459.6	1414.9	1370.2	1285.4	1222.7	1186.7	1153.0	1186.7
105°	1266.8	1509.5	1625.6	1647.7	1632.6	1617.5	1564.1	1520.0	1482.8	1477.0	1482.8
107.5°	1162.3	1439.9	1622.2	1712.7	1728.4	1744.1	1737.1	1716.2	1701.1	1688.3	1701.1
110°	1064.8	1330.7	1544.4	1690.7	1731.4	1772.0	1804.5	1813.8	1811.4	1809.1	1811.4

TEST NUMBER: P1011513

CATALOG NUMBER: S123DIP-B340D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	980.0	1222.7	1442.2	1610.5	1665.7	1720.9	1787.0	1820.7	1832.3	1833.5	1832.3
115°	915.0	1129.8	1331.9	1502.6	1565.8	1629.1	1716.2	1767.3	1790.5	1796.3	1790.5
117.5°	872.0	1057.8	1236.6	1393.4	1459.0	1524.6	1615.2	1672.1	1706.9	1715.1	1706.9
120°	839.5	1003.3	1160.0	1299.4	1358.0	1416.6	1508.4	1573.4	1601.3	1608.2	1601.3
122.5°	812.8	960.3	1098.5	1225.0	1278.4	1331.9	1410.8	1467.7	1499.1	1508.4	1499.1
125°	790.8	923.1	1049.7	1161.2	1207.6	1254.1	1328.4	1379.5	1408.5	1416.6	1408.5
127.5°	769.9	889.5	1004.4	1106.6	1149.6	1192.5	1259.9	1304.0	1330.7	1337.7	1330.7
130°	753.6	858.1	962.6	1056.7	1096.2	1135.6	1197.2	1239.0	1263.4	1272.6	1263.4
132.5°	738.5	829.1	923.1	1009.1	1046.2	1083.4	1140.3	1182.1	1203.0	1208.8	1203.0
135°	725.7	803.5	886.0	961.5	994.6	1027.6	1084.5	1119.4	1140.3	1148.4	1140.3
137.5°	714.1	779.1	848.8	916.2	945.8	975.4	1024.2	1060.2	1077.6	1084.5	1077.6
140°	703.7	758.2	817.5	873.2	898.2	923.1	967.3	999.8	1018.3	1017.2	1018.3
142.5°	694.4	738.5	787.3	833.7	854.6	875.5	911.5	939.4	955.6	954.5	955.6
145°	686.3	723.4	761.7	798.9	815.8	832.6	861.6	886.0	895.3	897.6	895.3
147.5°	678.1	710.6	742.0	773.3	785.5	797.7	820.9	838.4	847.7	848.8	847.7
150°	670.0	696.7	723.4	747.8	758.8	769.9	787.3	800.0	807.0	807.0	807.0
152.5°	660.7	683.9	706.0	726.9	735.6	744.3	757.1	768.7	772.2	772.2	772.2
155°	651.4	671.2	689.7	707.2	714.2	721.1	731.5	740.8	743.2	744.3	743.2
157.5°	641.0	657.2	673.5	687.4	693.2	699.0	708.3	715.3	717.6	717.6	717.6
160°	630.5	645.6	658.4	670.0	674.0	678.1	686.3	693.2	693.2	692.1	693.2
162.5°	620.1	631.7	642.1	652.6	656.0	659.5	664.2	670.0	670.0	668.8	670.0
165°	610.8	620.1	627.0	635.2	638.1	641.0	645.6	650.3	649.1	649.1	649.1
167.5°	601.5	609.6	615.4	620.1	622.4	624.7	627.0	630.5	629.4	629.4	629.4
170°	593.4	599.2	602.6	607.3	608.4	609.6	610.8	613.1	611.9	611.9	611.9
172.5°	585.2	589.9	592.2	595.7	596.2	596.8	596.8	599.2	596.8	595.7	596.8
175°	579.4	581.7	582.9	585.2	585.2	585.2	585.2	586.4	585.2	584.1	585.2
177.5°	574.8	575.9	577.1	578.3	578.3	578.3	577.1	578.3	575.9	575.9	575.9
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1011513

CATALOG NUMBER: S123DIP-B340D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2
2.5°	501.7	503.1	499.5	498.6	498.6	500.4	499.0	486.8	489.0	486.3	485.4
5°	557.1	554.4	550.7	548.9	546.6	540.3	539.8	525.8	523.1	514.0	509.9
7.5°	617.9	615.6	604.7	603.4	602.4	596.5	581.6	566.6	555.7	545.3	535.3
10°	687.3	680.5	675.5	665.5	660.5	652.3	632.8	618.8	600.2	584.3	563.4
12.5°	770.7	763.0	746.3	739.0	732.6	710.0	690.5	674.6	638.3	627.4	601.5
15°	832.0	815.7	813.8	798.0	797.1	772.1	734.9	717.7	689.5	649.6	622.9
17.5°	898.2	883.7	872.4	853.3	850.6	827.0	799.8	757.6	726.7	688.6	654.6
20°	946.8	939.1	919.5	911.8	896.0	876.0	847.9	795.7	758.0	719.9	678.2
22.5°	985.3	977.6	962.2	951.8	942.7	916.8	883.3	838.8	787.1	737.2	694.1
25°	984.9	982.6	976.3	971.3	964.5	945.4	917.3	874.6	817.0	762.1	702.2
27.5°	929.1	935.4	946.3	951.8	950.4	947.7	931.8	896.0	844.2	778.9	711.8
30°	812.9	836.1	856.5	883.7	891.9	911.8	920.9	900.5	859.2	798.4	724.0
32.5°	674.1	707.7	752.2	767.1	793.0	831.5	874.6	882.3	856.5	809.8	731.7
35°	553.0	580.7	615.1	638.7	661.9	724.5	778.9	826.1	834.7	803.9	729.9
37.5°	457.7	477.2	507.6	527.6	548.9	602.4	678.7	739.9	783.0	783.9	724.9
40°	388.8	397.4	423.7	438.2	458.6	504.9	573.0	652.8	715.9	744.9	711.8
42.5°	329.3	340.7	362.5	373.4	386.5	426.9	471.8	547.6	625.6	687.7	687.3
45°	294.0	302.1	312.1	321.2	336.2	360.2	411.5	468.2	543.0	613.3	641.0
47.5°	262.7	270.4	280.4	283.1	293.1	315.7	347.0	396.5	466.4	536.2	588.4
50°	236.4	242.7	249.5	254.5	259.0	277.6	301.2	343.0	398.8	466.4	531.2
52.5°	215.9	220.5	226.4	229.1	233.2	246.8	264.9	295.8	341.6	403.3	466.4
55°	196.9	200.1	203.7	208.2	210.0	220.0	234.1	260.4	294.4	349.8	409.6
57.5°	179.2	180.6	182.8	185.5	187.8	196.4	208.7	226.4	256.3	299.0	355.7
60°	159.2	162.9	164.2	166.9	168.3	175.1	184.6	199.6	222.7	259.5	302.1
62.5°	142.4	144.7	147.0	148.3	151.5	153.8	161.5	175.1	194.2	221.4	259.9
65°	127.5	128.4	129.7	131.1	132.0	134.7	142.0	151.1	165.6	189.6	219.6
67.5°	110.2	111.1	113.0	113.4	114.3	117.9	122.0	129.7	142.0	160.1	184.6
70°	93.5	94.8	95.7	96.6	98.0	99.3	103.9	110.2	119.8	132.5	151.5
72.5°	78.9	80.3	80.3	81.2	80.7	82.6	87.1	91.6	98.0	108.4	125.2
75°	64.4	64.4	65.3	65.8	66.2	68.0	69.9	73.5	78.5	86.6	97.1
77.5°	50.8	50.4	51.3	51.3	51.3	52.6	54.4	56.3	59.4	65.3	73.5
80°	37.2	37.2	38.1	38.6	37.7	38.1	39.0	40.8	43.1	47.2	51.7
82.5°	24.5	26.3	25.9	26.3	25.9	26.8	27.2	27.7	28.6	30.4	33.6
85°	15.0	15.0	15.0	15.4	15.0	15.4	15.4	15.4	15.9	16.8	18.1
87.5°	6.4	6.4	6.4	6.8	6.4	6.4	6.8	6.4	6.8	6.8	7.3
90°	33.7	32.5	33.7	32.6	31.4	30.2	29.0	27.9	29.0	25.5	22.1
92.5°	62.7	67.3	69.7	73.8	77.8	89.4	115.0	161.4	216.0	239.2	178.8
95°	147.5	157.9	180.0	200.9	221.8	283.3	418.0	558.5	688.6	613.1	422.7
97.5°	317.0	361.1	438.9	505.1	571.3	724.6	960.3	1095.0	1059.0	790.8	470.3
100°	772.2	856.9	974.2	1056.6	1139.1	1275.0	1369.0	1328.4	1099.6	743.2	437.8
102.5°	1222.7	1285.4	1370.2	1414.9	1459.6	1524.6	1504.9	1340.0	1024.2	673.5	409.9
105°	1520.0	1564.1	1617.5	1632.6	1647.7	1625.6	1509.5	1266.8	933.6	618.9	399.4
107.5°	1716.2	1737.1	1744.1	1728.4	1712.7	1622.2	1439.9	1162.3	853.5	579.4	397.1
110°	1813.8	1804.5	1772.0	1731.4	1690.7	1544.4	1330.7	1064.8	787.3	558.5	402.9

TEST NUMBER: P1011513

CATALOG NUMBER: S123DIP-B340D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1820.7	1787.0	1720.9	1665.7	1610.5	1442.2	1222.7	980.0	743.2	546.9	414.5
115°	1767.3	1716.2	1629.1	1565.8	1502.6	1331.9	1129.8	915.0	714.1	545.8	427.3
117.5°	1672.1	1615.2	1524.6	1459.0	1393.4	1236.6	1057.8	872.0	694.4	546.9	443.6
120°	1573.4	1508.4	1416.6	1358.0	1299.4	1160.0	1003.3	839.5	681.6	551.6	462.1
122.5°	1467.7	1410.8	1331.9	1278.4	1225.0	1098.5	960.3	812.8	673.5	559.7	479.6
125°	1379.5	1328.4	1254.1	1207.6	1161.2	1049.7	923.1	790.8	666.5	567.8	498.1
127.5°	1304.0	1259.9	1192.5	1149.6	1106.6	1004.4	889.5	769.9	663.0	577.1	513.2
130°	1239.0	1197.2	1135.6	1096.2	1056.7	962.6	858.1	753.6	659.5	586.4	528.3
132.5°	1182.1	1140.3	1083.4	1046.2	1009.1	923.1	829.1	738.5	658.4	593.4	542.3
135°	1119.4	1084.5	1027.6	994.6	961.5	886.0	803.5	725.7	657.2	600.3	553.9
137.5°	1060.2	1024.2	975.4	945.8	916.2	848.8	779.1	714.1	654.9	605.0	563.2
140°	999.8	967.3	923.1	898.2	873.2	817.5	758.2	703.7	653.7	609.6	570.1
142.5°	939.4	911.5	875.5	854.6	833.7	787.3	738.5	694.4	651.4	613.1	577.1
145°	886.0	861.6	832.6	815.8	798.9	761.7	723.4	686.3	649.1	614.3	581.7
147.5°	838.4	820.9	797.7	785.5	773.3	742.0	710.6	678.1	645.6	614.3	585.2
150°	800.0	787.3	769.9	758.8	747.8	723.4	696.7	670.0	641.0	614.3	586.4
152.5°	768.7	757.1	744.3	735.6	726.9	706.0	683.9	660.7	635.2	610.8	588.7
155°	740.8	731.5	721.1	714.2	707.2	689.7	671.2	651.4	628.2	608.5	588.7
157.5°	715.3	708.3	699.0	693.2	687.4	673.5	657.2	641.0	622.4	605.0	589.9
160°	693.2	686.3	678.1	674.0	670.0	658.4	645.6	630.5	615.4	602.6	589.9
162.5°	670.0	664.2	659.5	656.0	652.6	642.1	631.7	620.1	608.5	598.0	588.7
165°	650.3	645.6	641.0	638.1	635.2	627.0	620.1	610.8	601.5	593.4	586.4
167.5°	630.5	627.0	624.7	622.4	620.1	615.4	609.6	601.5	594.5	588.7	585.2
170°	613.1	610.8	609.6	608.4	607.3	602.6	599.2	593.4	587.6	584.1	581.7
172.5°	599.2	596.8	596.8	596.2	595.7	592.2	589.9	585.2	581.7	580.6	580.6
175°	586.4	585.2	585.2	585.2	585.2	582.9	581.7	579.4	577.1	577.1	578.3
177.5°	578.3	577.1	578.3	578.3	578.3	577.1	575.9	574.8	573.6	574.8	577.1
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1011513

CATALOG NUMBER: S123DIP-B340D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2
2.5°	480.9	479.5	479.5	478.6	475.9	470.9	470.4	471.3	468.6	465.9	461.8
5°	504.5	495.8	493.1	490.4	485.0	475.9	472.2	469.1	464.1	458.2	451.8
7.5°	524.4	512.2	508.5	503.6	492.7	480.0	471.8	465.0	458.2	450.0	442.3
10°	549.4	531.7	523.1	515.8	500.8	483.1	470.9	460.9	450.0	440.0	430.1
12.5°	577.5	548.9	546.2	528.5	511.3	485.0	470.0	455.5	440.9	428.7	418.3
15°	601.1	569.8	558.4	546.6	513.5	480.9	466.4	450.0	433.2	420.1	404.7
17.5°	616.1	590.2	566.2	550.3	515.8	486.8	458.6	440.0	422.3	404.2	391.5
20°	634.2	596.5	575.7	554.4	520.3	482.2	454.1	431.0	409.2	392.9	377.4
22.5°	652.3	601.5	584.3	561.2	521.2	477.7	445.9	422.8	397.9	381.5	364.7
25°	650.5	608.8	580.2	560.7	512.2	473.6	436.4	409.2	386.1	365.2	348.4
27.5°	651.9	600.6	571.6	548.9	505.8	467.7	426.4	397.9	373.8	352.0	334.3
30°	652.3	588.4	563.0	535.8	494.0	453.6	415.1	386.1	360.7	337.1	321.2
32.5°	651.0	578.4	546.6	522.2	475.4	440.0	401.9	371.1	345.2	323.5	308.5
35°	647.8	566.6	529.9	499.0	456.4	420.5	389.7	357.9	330.3	310.3	293.1
37.5°	639.2	553.9	512.2	481.8	434.1	397.9	370.6	344.3	317.6	294.0	279.4
40°	632.8	536.7	494.5	461.4	410.1	374.7	352.0	327.1	300.8	279.4	265.4
42.5°	618.3	520.3	476.3	436.9	386.5	350.2	328.9	308.9	286.3	265.4	252.7
45°	594.7	502.6	454.1	414.2	360.7	326.2	306.7	290.3	270.4	250.4	237.7
47.5°	561.6	477.2	430.5	390.6	335.2	300.3	280.8	268.6	252.7	235.9	225.0
50°	525.8	449.6	406.5	367.0	310.7	276.7	257.7	246.3	235.9	220.5	210.0
52.5°	479.1	420.1	378.8	341.1	284.4	251.8	235.0	226.8	215.9	205.0	196.0
55°	433.7	382.0	347.9	312.1	258.6	228.2	211.9	203.2	196.9	187.8	180.6
57.5°	381.1	346.6	315.3	282.6	234.5	206.9	191.4	181.0	176.9	172.8	166.0
60°	332.5	306.2	280.8	253.6	209.6	184.6	169.7	161.5	157.4	154.7	150.2
62.5°	288.1	267.7	245.9	224.1	184.2	161.5	150.2	142.0	138.4	137.9	133.8
65°	245.4	230.9	213.2	191.9	160.6	140.6	129.7	124.8	120.7	120.7	117.5
67.5°	202.8	192.8	178.7	163.8	139.3	120.7	110.7	106.2	103.9	103.9	101.6
70°	168.8	162.0	149.3	136.1	114.8	100.7	93.0	88.9	87.6	88.0	86.2
72.5°	137.0	129.7	119.3	109.8	93.9	83.5	78.0	73.5	71.2	71.7	71.2
75°	106.2	102.5	93.5	86.2	73.5	66.2	61.2	59.0	57.2	57.6	56.7
77.5°	79.8	74.4	69.4	64.4	56.7	50.8	46.7	44.5	43.1	43.1	43.1
80°	54.4	53.5	49.4	46.7	40.4	35.8	32.7	32.2	30.8	30.8	30.8
82.5°	35.4	33.1	30.8	29.0	25.4	22.7	21.3	20.4	20.0	19.5	20.4
85°	19.5	18.1	17.2	15.4	14.1	12.7	11.3	10.9	10.4	10.9	10.4
87.5°	7.7	6.4	6.4	5.9	5.4	5.0	5.0	4.1	4.1	3.6	3.6
90°	18.6	15.1	14.0	12.8	10.5	7.0	4.6	2.3	4.6	7.0	10.5
92.5°	117.3	80.1	69.6	59.2	47.6	37.2	25.5	17.4	25.5	37.2	47.6
95°	249.7	151.0	128.4	105.7	75.5	55.7	43.0	39.5	43.0	55.7	75.5
97.5°	269.4	171.9	146.9	121.9	91.7	74.3	63.9	62.7	63.9	74.3	91.7
100°	265.9	184.6	162.0	139.3	111.5	95.2	87.1	85.9	87.1	95.2	111.5
102.5°	270.6	199.7	179.4	159.1	134.7	119.6	112.6	110.3	112.6	119.6	134.7
105°	279.8	217.1	199.1	181.1	159.1	145.1	138.2	134.7	138.2	145.1	159.1
107.5°	294.9	239.2	222.4	205.5	184.6	170.7	163.7	160.2	163.7	170.7	184.6
110°	314.7	262.4	246.2	229.9	210.2	197.4	191.6	188.1	191.6	197.4	210.2

TEST NUMBER: P1011513

CATALOG NUMBER: S123DIP-B340D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	334.4	286.8	271.2	255.5	235.7	222.9	217.1	213.7	217.1	222.9	235.7
115°	356.5	312.4	296.7	281.0	261.3	249.7	242.7	238.0	242.7	249.7	261.3
117.5°	379.7	335.6	321.0	306.5	284.5	274.0	268.2	262.4	268.2	274.0	284.5
120°	401.8	360.0	345.4	330.9	308.9	297.3	291.5	288.0	291.5	297.3	308.9
122.5°	425.0	384.3	368.6	353.0	332.1	319.3	313.5	310.0	313.5	319.3	332.1
125°	447.1	406.4	390.8	375.1	353.0	340.2	333.3	330.9	333.3	340.2	353.0
127.5°	466.8	427.3	411.6	396.0	371.6	358.8	350.7	347.2	350.7	358.8	371.6
130°	484.2	445.9	430.2	414.5	390.2	376.2	365.8	362.3	365.8	376.2	390.2
132.5°	499.3	462.1	447.0	432.0	407.6	390.2	378.5	373.9	378.5	390.2	407.6
135°	514.4	478.4	462.8	447.1	422.7	405.2	392.5	387.8	392.5	405.2	422.7
137.5°	524.9	490.0	475.5	461.0	436.6	418.0	405.2	400.6	405.2	418.0	436.6
140°	535.3	501.6	487.1	472.6	449.4	430.8	419.2	413.4	419.2	430.8	449.4
142.5°	543.4	510.9	497.6	484.2	461.0	444.7	432.0	427.3	432.0	444.7	461.0
145°	550.4	520.2	506.8	493.5	473.8	456.3	445.9	442.4	445.9	456.3	473.8
147.5°	556.2	528.3	516.7	505.1	485.4	470.3	459.8	457.5	459.8	470.3	485.4
150°	562.0	535.3	524.8	514.4	498.1	483.0	473.8	472.6	473.8	483.0	498.1
152.5°	565.5	543.4	533.6	523.7	509.8	497.0	487.7	487.7	487.7	497.0	509.8
155°	570.1	550.4	542.2	534.1	521.4	509.8	502.8	502.8	502.8	509.8	521.4
157.5°	572.5	556.2	549.8	543.4	531.8	521.4	515.6	514.4	515.6	521.4	531.8
160°	575.9	562.0	556.2	550.4	542.3	533.0	528.3	528.3	528.3	533.0	542.3
162.5°	577.1	565.5	560.8	556.2	549.2	542.3	538.8	538.8	538.8	542.3	549.2
165°	578.3	569.0	564.9	560.8	556.2	550.4	548.1	549.2	548.1	550.4	556.2
167.5°	578.3	571.3	568.4	565.5	562.0	557.4	556.2	557.4	556.2	557.4	562.0
170°	577.1	571.3	570.2	569.0	566.7	563.2	562.0	564.3	562.0	563.2	566.7
172.5°	577.1	572.5	571.9	571.3	570.1	567.8	567.8	569.0	567.8	567.8	570.1
175°	575.9	573.6	573.0	572.5	572.5	570.1	571.3	572.5	571.3	570.1	572.5
177.5°	574.8	573.6	573.6	573.6	573.6	572.5	573.6	574.8	573.6	572.5	573.6
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1011513

CATALOG NUMBER: S123DIP-B340D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2
2.5°	460.9	460.5	461.4	458.6	454.1	451.8	445.5	444.1	443.7	444.1	444.6
5°	448.2	447.8	446.4	441.9	436.4	432.3	424.6	424.2	421.4	418.7	420.1
7.5°	436.0	434.1	431.4	425.5	418.3	413.7	407.4	402.8	399.2	396.9	395.1
10°	423.7	421.0	418.3	410.6	401.5	394.7	387.0	383.3	379.3	377.4	375.6
12.5°	407.8	405.1	400.1	391.0	385.6	377.0	369.3	365.6	363.4	359.7	357.5
15°	395.1	389.7	387.0	377.4	366.1	365.2	351.1	350.2	345.7	345.7	342.1
17.5°	380.6	376.5	371.5	362.0	353.8	345.7	338.4	335.7	331.6	330.7	328.9
20°	366.5	361.1	359.3	349.8	341.1	331.2	323.5	320.7	318.9	317.1	318.5
22.5°	352.0	347.5	343.0	334.3	328.0	318.0	313.5	310.7	308.0	307.1	307.6
25°	338.0	333.9	329.3	320.7	313.9	305.8	301.7	300.3	299.0	299.0	298.5
27.5°	324.4	320.3	316.2	308.5	301.7	295.8	292.6	291.2	289.9	290.8	291.7
30°	310.3	306.7	303.0	296.2	290.8	285.3	283.5	282.6	282.2	284.4	284.4
32.5°	297.6	294.4	291.7	285.3	279.9	275.4	274.0	274.5	274.9	276.3	277.2
35°	284.4	282.2	279.4	274.0	269.5	265.4	265.8	265.8	266.7	269.0	270.8
37.5°	272.6	269.5	267.2	262.7	259.0	255.4	256.8	258.1	259.0	261.8	262.7
40°	258.6	257.2	255.4	250.9	247.7	247.2	247.7	248.6	250.4	251.8	253.1
42.5°	247.2	245.4	243.2	239.5	236.8	237.3	237.7	238.6	239.5	241.8	243.2
45°	234.5	233.2	231.4	228.2	225.9	226.4	226.8	226.8	227.7	230.5	231.4
47.5°	220.5	220.9	218.7	215.5	214.1	214.1	214.1	215.0	217.3	218.2	218.7
50°	206.9	206.0	205.5	202.3	201.4	201.0	201.4	201.9	205.0	204.6	206.0
52.5°	192.3	192.3	191.9	190.1	188.7	188.7	187.8	190.1	191.0	191.9	193.3
55°	178.3	176.9	176.5	175.6	173.7	173.3	174.2	176.9	177.8	178.7	180.1
57.5°	162.9	162.9	162.0	160.6	160.6	160.6	160.6	162.4	163.8	164.7	167.4
60°	148.8	147.0	145.6	145.6	145.6	145.2	147.9	147.9	150.6	151.1	152.0
62.5°	132.0	131.1	130.2	130.7	130.2	131.1	132.0	133.8	134.3	135.6	137.0
65°	116.1	116.1	115.2	117.9	116.1	116.1	118.4	118.4	119.3	120.7	122.5
67.5°	100.7	101.2	100.3	100.3	101.2	101.6	102.1	103.9	104.3	106.2	108.4
70°	84.8	85.7	86.2	85.3	86.2	87.1	88.0	88.5	90.3	91.2	92.5
72.5°	70.8	71.7	70.3	70.8	71.2	72.1	72.6	73.5	74.4	77.1	78.0
75°	56.7	56.3	55.8	57.6	56.7	58.5	59.0	59.0	59.9	62.1	63.1
77.5°	43.6	43.6	44.0	43.1	44.5	44.0	44.5	45.8	47.2	47.2	50.8
80°	30.4	31.3	31.3	31.3	31.8	32.2	31.3	33.6	34.0	34.0	35.4
82.5°	19.5	20.0	19.5	20.4	20.4	21.3	20.9	21.3	22.2	23.1	23.6
85°	10.4	10.4	11.3	11.3	10.9	11.3	10.9	11.3	12.2	12.2	12.7
87.5°	3.6	3.6	3.6	3.6	4.1	3.6	4.1	4.1	3.6	3.6	5.0
90°	12.8	14.0	15.1	18.6	22.1	25.5	29.0	27.9	29.0	30.2	31.4
92.5°	59.2	69.6	80.1	117.3	178.8	239.2	216.0	161.4	115.0	89.4	77.8
95°	105.7	128.4	151.0	249.7	422.7	613.1	688.6	558.5	418.0	283.3	221.8
97.5°	121.9	146.9	171.9	269.4	470.3	790.8	1059.0	1095.0	960.3	724.6	571.3
100°	139.3	162.0	184.6	265.9	437.8	743.2	1099.6	1328.4	1369.0	1275.0	1139.1
102.5°	159.1	179.4	199.7	270.6	409.9	673.5	1024.2	1340.0	1504.9	1524.6	1459.6
105°	181.1	199.1	217.1	279.8	399.4	618.9	933.6	1266.8	1509.5	1625.6	1647.7
107.5°	205.5	222.4	239.2	294.9	397.1	579.4	853.5	1162.3	1439.9	1622.2	1712.7
110°	229.9	246.2	262.4	314.7	402.9	558.5	787.3	1064.8	1330.7	1544.4	1690.7

TEST NUMBER: P1011513

CATALOG NUMBER: S123DIP-B340D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	255.5	271.2	286.8	334.4	414.5	546.9	743.2	980.0	1222.7	1442.2	1610.5
115°	281.0	296.7	312.4	356.5	427.3	545.8	714.1	915.0	1129.8	1331.9	1502.6
117.5°	306.5	321.0	335.6	379.7	443.6	546.9	694.4	872.0	1057.8	1236.6	1393.4
120°	330.9	345.4	360.0	401.8	462.1	551.6	681.6	839.5	1003.3	1160.0	1299.4
122.5°	353.0	368.6	384.3	425.0	479.6	559.7	673.5	812.8	960.3	1098.5	1225.0
125°	375.1	390.8	406.4	447.1	498.1	567.8	666.5	790.8	923.1	1049.7	1161.2
127.5°	396.0	411.6	427.3	466.8	513.2	577.1	663.0	769.9	889.5	1004.4	1106.6
130°	414.5	430.2	445.9	484.2	528.3	586.4	659.5	753.6	858.1	962.6	1056.7
132.5°	432.0	447.0	462.1	499.3	542.3	593.4	658.4	738.5	829.1	923.1	1009.1
135°	447.1	462.8	478.4	514.4	553.9	600.3	657.2	725.7	803.5	886.0	961.5
137.5°	461.0	475.5	490.0	524.9	563.2	605.0	654.9	714.1	779.1	848.8	916.2
140°	472.6	487.1	501.6	535.3	570.1	609.6	653.7	703.7	758.2	817.5	873.2
142.5°	484.2	497.6	510.9	543.4	577.1	613.1	651.4	694.4	738.5	787.3	833.7
145°	493.5	506.8	520.2	550.4	581.7	614.3	649.1	686.3	723.4	761.7	798.9
147.5°	505.1	516.7	528.3	556.2	585.2	614.3	645.6	678.1	710.6	742.0	773.3
150°	514.4	524.8	535.3	562.0	586.4	614.3	641.0	670.0	696.7	723.4	747.8
152.5°	523.7	533.6	543.4	565.5	588.7	610.8	635.2	660.7	683.9	706.0	726.9
155°	534.1	542.2	550.4	570.1	588.7	608.5	628.2	651.4	671.2	689.7	707.2
157.5°	543.4	549.8	556.2	572.5	589.9	605.0	622.4	641.0	657.2	673.5	687.4
160°	550.4	556.2	562.0	575.9	589.9	602.6	615.4	630.5	645.6	658.4	670.0
162.5°	556.2	560.8	565.5	577.1	588.7	598.0	608.5	620.1	631.7	642.1	652.6
165°	560.8	564.9	569.0	578.3	586.4	593.4	601.5	610.8	620.1	627.0	635.2
167.5°	565.5	568.4	571.3	578.3	585.2	588.7	594.5	601.5	609.6	615.4	620.1
170°	569.0	570.2	571.3	577.1	581.7	584.1	587.6	593.4	599.2	602.6	607.3
172.5°	571.3	571.9	572.5	577.1	580.6	580.6	581.7	585.2	589.9	592.2	595.7
175°	572.5	573.0	573.6	575.9	578.3	577.1	577.1	579.4	581.7	582.9	585.2
177.5°	573.6	573.6	573.6	574.8	577.1	574.8	573.6	574.8	575.9	577.1	578.3
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1011513

CATALOG NUMBER: S123DIP-B340D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2
2.5°	444.1	444.6	442.8	441.4	445.0	442.8	442.8	443.2	442.3	443.7	443.2
5°	419.2	419.6	416.4	417.4	415.5	415.1	414.6	417.4	416.9	416.4	417.4
7.5°	394.7	394.7	393.3	392.4	392.4	391.0	392.9	392.4	393.3	393.3	394.7
10°	374.3	375.2	372.9	370.6	370.2	370.6	370.6	371.1	371.5	374.7	374.3
12.5°	357.5	356.1	355.7	354.3	352.0	351.1	350.2	355.2	353.8	353.8	353.8
15°	338.9	342.1	341.6	337.5	336.6	338.4	337.5	337.5	342.1	341.6	341.1
17.5°	328.9	328.0	327.1	324.8	325.3	324.8	325.3	325.3	328.0	328.0	328.0
20°	317.6	315.7	315.7	314.8	314.8	313.5	315.3	315.7	317.6	317.6	318.0
22.5°	307.6	306.2	306.2	305.8	306.7	304.9	306.7	307.1	307.1	308.5	308.5
25°	299.0	298.0	298.0	299.0	299.0	299.0	299.0	300.8	299.4	299.9	299.4
27.5°	291.2	291.7	292.2	292.6	292.2	292.6	293.1	294.0	294.4	294.0	293.1
30°	284.0	285.3	285.8	285.8	286.7	287.2	287.6	287.6	288.1	286.7	287.6
32.5°	278.5	278.5	279.4	279.9	280.8	281.3	281.3	282.2	281.7	280.4	280.8
35°	270.8	270.8	272.6	273.6	274.9	274.5	274.9	274.9	275.4	274.5	273.1
37.5°	263.1	264.0	264.0	265.8	266.3	266.7	266.3	267.2	266.7	265.8	265.4
40°	254.0	253.6	254.0	255.4	255.9	255.9	255.9	256.8	256.8	256.8	256.3
42.5°	242.7	244.1	243.6	245.0	244.5	244.5	245.4	246.3	246.8	245.4	245.9
45°	231.8	231.8	232.7	232.7	233.2	233.2	235.0	234.1	235.0	234.1	234.5
47.5°	220.0	220.5	220.5	220.9	221.8	222.7	221.8	222.3	222.3	222.7	221.8
50°	206.9	206.9	207.8	209.1	210.9	210.0	209.6	211.4	210.0	210.0	209.1
52.5°	193.3	194.6	195.1	196.4	197.8	198.2	198.7	197.8	198.2	196.9	197.3
55°	180.1	180.6	182.4	183.7	185.1	185.1	184.6	185.1	185.5	183.7	183.7
57.5°	166.9	168.3	170.1	170.1	171.9	171.9	171.5	171.5	171.9	170.6	170.1
60°	152.9	154.2	156.5	156.5	159.2	159.7	158.8	157.9	157.9	156.5	157.0
62.5°	137.9	139.3	140.6	142.9	144.7	143.8	145.6	143.8	144.3	141.5	141.5
65°	124.8	125.2	127.5	129.7	129.7	130.7	129.7	130.2	128.8	128.8	127.0
67.5°	109.3	109.3	111.6	113.9	116.1	116.1	116.1	114.8	114.8	113.4	113.4
70°	95.7	95.3	97.5	98.9	100.3	100.7	99.8	99.3	98.4	97.1	96.6
72.5°	78.9	79.8	82.1	83.0	85.3	84.8	87.1	84.4	84.4	82.1	81.7
75°	64.0	64.9	67.1	68.5	69.9	69.9	71.2	69.9	68.0	67.1	66.7
77.5°	50.8	50.4	52.2	54.4	54.9	54.4	55.3	54.9	53.1	53.1	52.2
80°	36.3	37.7	39.5	39.0	40.8	40.4	40.4	39.5	39.5	38.1	39.0
82.5°	24.0	25.4	25.9	25.4	25.9	26.8	27.2	26.8	26.8	25.9	26.3
85°	12.7	12.7	13.6	14.1	13.6	13.6	14.1	15.4	14.5	13.6	14.5
87.5°	4.1	3.6	3.6	4.1	3.6	3.6	4.1	4.1	4.5	4.5	4.5
90°	32.6	33.7	32.5	33.7	34.8	33.7	34.8	33.7	32.5	33.7	32.6
92.5°	73.8	69.7	67.3	62.7	63.9	61.5	63.9	62.7	67.3	69.7	73.8
95°	200.9	180.0	157.9	147.5	139.3	134.7	139.3	147.5	157.9	180.0	200.9
97.5°	505.1	438.9	361.1	317.0	289.1	276.4	289.1	317.0	361.1	438.9	505.1
100°	1056.6	974.2	856.9	772.2	726.9	728.1	726.9	772.2	856.9	974.2	1056.6
102.5°	1414.9	1370.2	1285.4	1222.7	1186.7	1153.0	1186.7	1222.7	1285.4	1370.2	1414.9
105°	1632.6	1617.5	1564.1	1520.0	1482.8	1477.0	1482.8	1520.0	1564.1	1617.5	1632.6
107.5°	1728.4	1744.1	1737.1	1716.2	1701.1	1688.3	1701.1	1716.2	1737.1	1744.1	1728.4
110°	1731.4	1772.0	1804.5	1813.8	1811.4	1809.1	1811.4	1813.8	1804.5	1772.0	1731.4

TEST NUMBER: P1011513

CATALOG NUMBER: S123DIP-B340D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1665.7	1720.9	1787.0	1820.7	1832.3	1833.5	1832.3	1820.7	1787.0	1720.9	1665.7
115°	1565.8	1629.1	1716.2	1767.3	1790.5	1796.3	1790.5	1767.3	1716.2	1629.1	1565.8
117.5°	1459.0	1524.6	1615.2	1672.1	1706.9	1715.1	1706.9	1672.1	1615.2	1524.6	1459.0
120°	1358.0	1416.6	1508.4	1573.4	1601.3	1608.2	1601.3	1573.4	1508.4	1416.6	1358.0
122.5°	1278.4	1331.9	1410.8	1467.7	1499.1	1508.4	1499.1	1467.7	1410.8	1331.9	1278.4
125°	1207.6	1254.1	1328.4	1379.5	1408.5	1416.6	1408.5	1379.5	1328.4	1254.1	1207.6
127.5°	1149.6	1192.5	1259.9	1304.0	1330.7	1337.7	1330.7	1304.0	1259.9	1192.5	1149.6
130°	1096.2	1135.6	1197.2	1239.0	1263.4	1272.6	1263.4	1239.0	1197.2	1135.6	1096.2
132.5°	1046.2	1083.4	1140.3	1182.1	1203.0	1208.8	1203.0	1182.1	1140.3	1083.4	1046.2
135°	994.6	1027.6	1084.5	1119.4	1140.3	1148.4	1140.3	1119.4	1084.5	1027.6	994.6
137.5°	945.8	975.4	1024.2	1060.2	1077.6	1084.5	1077.6	1060.2	1024.2	975.4	945.8
140°	898.2	923.1	967.3	999.8	1018.3	1017.2	1018.3	999.8	967.3	923.1	898.2
142.5°	854.6	875.5	911.5	939.4	955.6	954.5	955.6	939.4	911.5	875.5	854.6
145°	815.8	832.6	861.6	886.0	895.3	897.6	895.3	886.0	861.6	832.6	815.8
147.5°	785.5	797.7	820.9	838.4	847.7	848.8	847.7	838.4	820.9	797.7	785.5
150°	758.8	769.9	787.3	800.0	807.0	807.0	807.0	800.0	787.3	769.9	758.8
152.5°	735.6	744.3	757.1	768.7	772.2	772.2	772.2	768.7	757.1	744.3	735.6
155°	714.2	721.1	731.5	740.8	743.2	744.3	743.2	740.8	731.5	721.1	714.2
157.5°	693.2	699.0	708.3	715.3	717.6	717.6	717.6	715.3	708.3	699.0	693.2
160°	674.0	678.1	686.3	693.2	693.2	692.1	693.2	693.2	686.3	678.1	674.0
162.5°	656.0	659.5	664.2	670.0	670.0	668.8	670.0	670.0	664.2	659.5	656.0
165°	638.1	641.0	645.6	650.3	649.1	649.1	649.1	650.3	645.6	641.0	638.1
167.5°	622.4	624.7	627.0	630.5	629.4	629.4	629.4	630.5	627.0	624.7	622.4
170°	608.4	609.6	610.8	613.1	611.9	611.9	611.9	613.1	610.8	609.6	608.4
172.5°	596.2	596.8	596.8	599.2	596.8	595.7	596.8	599.2	596.8	596.8	596.2
175°	585.2	585.2	585.2	586.4	585.2	584.1	585.2	586.4	585.2	585.2	585.2
177.5°	578.3	578.3	577.1	578.3	575.9	575.9	575.9	578.3	577.1	578.3	578.3
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1011513

CATALOG NUMBER: S123DIP-B340D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2	468.2
2.5°	444.6	445.5	445.9	444.1	442.8	445.0	448.2	450.5	452.3	454.6	455.9
5°	418.3	421.4	421.4	422.3	423.7	426.0	431.9	436.0	439.6	442.3	444.6
7.5°	396.0	398.3	399.7	401.9	404.2	407.4	414.2	420.1	425.5	428.7	432.3
10°	376.1	377.9	380.2	381.5	385.6	390.1	398.8	403.7	410.1	415.1	419.6
12.5°	357.0	363.4	364.7	364.3	367.9	372.9	381.5	389.2	396.0	401.0	406.0
15°	343.4	345.7	348.4	347.9	355.7	357.0	364.3	373.4	382.4	385.6	390.1
17.5°	328.4	332.1	334.8	336.2	338.4	343.4	350.2	357.0	368.8	369.3	381.1
20°	316.6	320.3	322.1	323.9	325.3	331.2	337.1	344.8	354.3	359.3	365.6
22.5°	308.9	310.7	312.1	313.5	315.3	318.5	325.7	334.3	340.7	346.1	350.2
25°	299.9	301.7	303.5	304.4	305.8	307.6	313.0	319.8	328.9	332.5	336.6
27.5°	293.5	293.5	294.4	294.4	296.2	298.0	302.1	308.5	315.7	320.3	325.7
30°	286.7	286.3	286.7	286.3	285.8	288.5	292.2	297.6	302.6	308.0	311.7
32.5°	279.9	279.4	279.4	279.9	278.1	279.4	281.3	286.3	291.7	294.4	298.5
35°	272.6	271.7	271.7	271.7	270.8	269.9	271.7	276.3	279.9	283.5	286.7
37.5°	265.4	264.0	264.0	263.1	262.2	260.8	260.8	264.5	269.5	270.8	274.9
40°	255.4	255.4	254.5	254.0	253.1	252.2	250.9	254.0	258.6	259.9	263.1
42.5°	245.4	244.1	243.6	243.6	243.6	242.2	241.3	243.6	246.3	248.6	250.4
45°	234.1	233.2	233.6	233.2	232.3	231.8	231.4	232.3	235.4	236.4	238.6
47.5°	221.8	221.4	221.4	220.9	220.5	220.9	219.1	221.4	222.3	223.2	225.0
50°	209.1	208.7	208.2	207.8	207.8	208.2	207.8	207.8	209.6	210.5	212.3
52.5°	196.4	195.1	195.1	194.6	194.6	193.7	194.6	195.1	196.0	196.9	197.8
55°	182.8	182.8	181.5	181.5	180.6	180.6	181.0	180.6	182.4	183.3	183.3
57.5°	169.7	167.9	168.3	167.4	166.5	166.0	166.0	166.9	167.9	167.9	168.8
60°	155.6	153.8	153.3	151.5	152.4	151.1	151.5	151.5	153.3	152.4	153.3
62.5°	141.5	139.3	137.9	137.0	137.0	137.5	136.5	136.1	137.0	137.9	139.7
65°	126.6	125.2	123.8	122.5	122.5	122.0	122.9	121.6	121.1	121.6	122.5
67.5°	111.1	109.8	108.4	107.1	107.5	106.2	105.2	106.6	105.7	106.2	107.1
70°	96.2	95.3	92.5	91.6	91.2	91.6	91.2	90.3	91.6	91.2	91.6
72.5°	81.2	80.3	78.9	76.7	76.7	76.2	75.8	75.8	75.3	75.3	75.3
75°	66.7	64.9	63.5	63.1	62.1	61.7	61.2	60.3	60.8	61.2	60.3
77.5°	51.7	49.4	49.0	49.0	47.6	47.6	48.1	47.6	47.2	47.2	47.2
80°	38.1	36.3	36.3	35.4	34.5	34.5	34.5	34.5	34.0	33.6	34.0
82.5°	24.5	24.0	23.6	23.6	24.5	22.7	23.6	23.1	22.7	22.7	22.2
85°	13.6	14.1	13.6	14.1	13.2	13.6	13.6	13.6	13.2	13.6	12.7
87.5°	5.0	5.0	5.0	5.4	5.4	5.4	5.4	5.4	5.9	5.4	5.4
90°	31.4	30.2	29.0	27.9	29.0	25.5	22.1	18.6	15.1	14.0	12.8
92.5°	77.8	89.4	115.0	161.4	216.0	239.2	178.8	117.3	80.1	69.6	59.2
95°	221.8	283.3	418.0	558.5	688.6	613.1	422.7	249.7	151.0	128.4	105.7
97.5°	571.3	724.6	960.3	1095.0	1059.0	790.8	470.3	269.4	171.9	146.9	121.9
100°	1139.1	1275.0	1369.0	1328.4	1099.6	743.2	437.8	265.9	184.6	162.0	139.3
102.5°	1459.6	1524.6	1504.9	1340.0	1024.2	673.5	409.9	270.6	199.7	179.4	159.1
105°	1647.7	1625.6	1509.5	1266.8	933.6	618.9	399.4	279.8	217.1	199.1	181.1
107.5°	1712.7	1622.2	1439.9	1162.3	853.5	579.4	397.1	294.9	239.2	222.4	205.5
110°	1690.7	1544.4	1330.7	1064.8	787.3	558.5	402.9	314.7	262.4	246.2	229.9

TEST NUMBER: P1011513

CATALOG NUMBER: S123DIP-B340D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1610.5	1442.2	1222.7	980.0	743.2	546.9	414.5	334.4	286.8	271.2	255.5
115°	1502.6	1331.9	1129.8	915.0	714.1	545.8	427.3	356.5	312.4	296.7	281.0
117.5°	1393.4	1236.6	1057.8	872.0	694.4	546.9	443.6	379.7	335.6	321.0	306.5
120°	1299.4	1160.0	1003.3	839.5	681.6	551.6	462.1	401.8	360.0	345.4	330.9
122.5°	1225.0	1098.5	960.3	812.8	673.5	559.7	479.6	425.0	384.3	368.6	353.0
125°	1161.2	1049.7	923.1	790.8	666.5	567.8	498.1	447.1	406.4	390.8	375.1
127.5°	1106.6	1004.4	889.5	769.9	663.0	577.1	513.2	466.8	427.3	411.6	396.0
130°	1056.7	962.6	858.1	753.6	659.5	586.4	528.3	484.2	445.9	430.2	414.5
132.5°	1009.1	923.1	829.1	738.5	658.4	593.4	542.3	499.3	462.1	447.0	432.0
135°	961.5	886.0	803.5	725.7	657.2	600.3	553.9	514.4	478.4	462.8	447.1
137.5°	916.2	848.8	779.1	714.1	654.9	605.0	563.2	524.9	490.0	475.5	461.0
140°	873.2	817.5	758.2	703.7	653.7	609.6	570.1	535.3	501.6	487.1	472.6
142.5°	833.7	787.3	738.5	694.4	651.4	613.1	577.1	543.4	510.9	497.6	484.2
145°	798.9	761.7	723.4	686.3	649.1	614.3	581.7	550.4	520.2	506.8	493.5
147.5°	773.3	742.0	710.6	678.1	645.6	614.3	585.2	556.2	528.3	516.7	505.1
150°	747.8	723.4	696.7	670.0	641.0	614.3	586.4	562.0	535.3	524.8	514.4
152.5°	726.9	706.0	683.9	660.7	635.2	610.8	588.7	565.5	543.4	533.6	523.7
155°	707.2	689.7	671.2	651.4	628.2	608.5	588.7	570.1	550.4	542.2	534.1
157.5°	687.4	673.5	657.2	641.0	622.4	605.0	589.9	572.5	556.2	549.8	543.4
160°	670.0	658.4	645.6	630.5	615.4	602.6	589.9	575.9	562.0	556.2	550.4
162.5°	652.6	642.1	631.7	620.1	608.5	598.0	588.7	577.1	565.5	560.8	556.2
165°	635.2	627.0	620.1	610.8	601.5	593.4	586.4	578.3	569.0	564.9	560.8
167.5°	620.1	615.4	609.6	601.5	594.5	588.7	585.2	578.3	571.3	568.4	565.5
170°	607.3	602.6	599.2	593.4	587.6	584.1	581.7	577.1	571.3	570.2	569.0
172.5°	595.7	592.2	589.9	585.2	581.7	580.6	580.6	577.1	572.5	571.9	571.3
175°	585.2	582.9	581.7	579.4	577.1	577.1	578.3	575.9	573.6	573.0	572.5
177.5°	578.3	577.1	575.9	574.8	573.6	574.8	577.1	574.8	573.6	573.6	573.6
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1011513

CATALOG NUMBER: S123DIP-B340D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	468.2	468.2	468.2	468.2
2.5°	458.2	459.5	464.1	469.5
5°	449.1	452.7	459.1	467.7
7.5°	439.1	444.6	453.6	464.5
10°	427.8	435.5	446.8	460.5
12.5°	415.5	425.5	440.0	454.1
15°	407.8	417.8	431.0	446.4
17.5°	392.9	404.7	418.3	440.0
20°	377.4	390.6	408.3	430.1
22.5°	365.6	379.7	396.5	419.6
25°	351.6	366.1	384.2	408.3
27.5°	336.6	351.1	371.5	396.9
30°	325.3	339.3	358.8	386.1
32.5°	311.7	325.3	345.7	374.3
35°	296.2	311.7	331.2	360.2
37.5°	284.4	298.5	318.9	346.6
40°	271.7	284.0	303.9	331.2
42.5°	258.1	271.7	289.0	316.2
45°	245.4	255.4	273.1	299.0
47.5°	231.8	243.2	256.8	276.7
50°	217.3	226.8	241.8	255.4
52.5°	203.2	210.9	223.6	234.1
55°	188.3	196.0	205.5	211.9
57.5°	174.2	179.6	186.0	190.1
60°	157.0	162.4	166.5	170.6
62.5°	141.5	145.6	147.9	150.2
65°	125.7	127.9	129.3	131.1
67.5°	108.4	110.7	111.1	113.9
70°	92.5	93.0	93.9	95.3
72.5°	77.6	78.5	78.0	78.9
75°	62.1	63.1	62.1	63.1
77.5°	47.2	48.1	48.1	49.4
80°	34.0	34.5	34.9	34.9
82.5°	22.2	23.6	22.7	23.1
85°	12.7	13.2	13.2	13.6
87.5°	5.9	6.4	5.9	6.8
90°	10.5	7.0	4.6	2.3
92.5°	47.6	37.2	25.5	17.4
95°	75.5	55.7	43.0	39.5
97.5°	91.7	74.3	63.9	62.7
100°	111.5	95.2	87.1	85.9
102.5°	134.7	119.6	112.6	110.3
105°	159.1	145.1	138.2	134.7
107.5°	184.6	170.7	163.7	160.2
110°	210.2	197.4	191.6	188.1

TEST NUMBER: P1011513

CATALOG NUMBER: S123DIP-B340D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	235.7	222.9	217.1	213.7
115°	261.3	249.7	242.7	238.0
117.5°	284.5	274.0	268.2	262.4
120°	308.9	297.3	291.5	288.0
122.5°	332.1	319.3	313.5	310.0
125°	353.0	340.2	333.3	330.9
127.5°	371.6	358.8	350.7	347.2
130°	390.2	376.2	365.8	362.3
132.5°	407.6	390.2	378.5	373.9
135°	422.7	405.2	392.5	387.8
137.5°	436.6	418.0	405.2	400.6
140°	449.4	430.8	419.2	413.4
142.5°	461.0	444.7	432.0	427.3
145°	473.8	456.3	445.9	442.4
147.5°	485.4	470.3	459.8	457.5
150°	498.1	483.0	473.8	472.6
152.5°	509.8	497.0	487.7	487.7
155°	521.4	509.8	502.8	502.8
157.5°	531.8	521.4	515.6	514.4
160°	542.3	533.0	528.3	528.3
162.5°	549.2	542.3	538.8	538.8
165°	556.2	550.4	548.1	549.2
167.5°	562.0	557.4	556.2	557.4
170°	566.7	563.2	562.0	564.3
172.5°	570.1	567.8	567.8	569.0
175°	572.5	570.1	571.3	572.5
177.5°	573.6	572.5	573.6	574.8
180°	573.6	573.6	573.6	573.6

(END OF REPORT)