

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011567

Luminaire Tested: S123DIP-B340D365UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011567
REPORT IS A COMBINATION OF REPORTS P989774 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D365UB35-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2747.0 lumens
Efficiency: N/A
Efficacy: 123.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011567

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1011567

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	58	58	52
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	51	50	49	49	49	44
2	90	83	77	72	83	77	71	67	65	62	58	55	52	50	46	44	42	42	42	37
3	82	73	66	60	76	68	61	56	58	53	49	49	45	42	41	38	36	36	36	32
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	36	34	31	31	31	28
5	69	58	50	44	64	54	47	41	46	41	36	39	35	32	33	30	27	27	27	24
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24	24	24	21
7	59	47	39	33	54	44	37	32	38	32	28	32	28	25	27	24	21	21	21	19
8	55	42	35	29	51	40	33	28	35	29	25	30	25	22	25	22	19	19	19	17
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	17	17	15
10	48	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5061	5061	5061	5061
5°	5064	5831	5079	4352
10°	5032	7056	5037	3800
15°	4962	8368	5002	3421
20°	4903	9634	4913	3148
25°	4813	9878	4824	3005
30°	4750	8161	4750	2912
35°	4671	5458	4641	2829
40°	4577	3940	4521	2703
45°	4458	3121	4331	2547
50°	4171	2650	4023	2392
55°	3856	2329	3698	2220
60°	3535	2028	3347	2040
65°	3184	1736	3029	1799
70°	2818	1441	2630	1516
75°	2408	1086	2252	1171
80°	1906	726	1754	768
85°	1316	332	1047	304

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 8162 cd/sqm

TEST NUMBER: P1011567

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.2	1.7
10°-20°	148.5	5.4
20°-30°	249.9	9.1
30°-40°	282.4	10.3
40°-50°	252.9	9.2
50°-60°	204.2	7.4
60°-70°	142.3	5.2
70°-80°	74.7	2.7
80°-90°	18.9	0.7
90°-100°	95.7	3.5
100°-110°	280.3	10.2
110°-120°	273.7	10.0
120°-130°	218.0	7.9
130°-140°	172.0	6.3
140°-150°	128.3	4.7
150°-160°	89.4	3.3
160°-170°	52.5	1.9
170°-180°	17.1	0.6
0°-30°	444.6	16.2
0°-40°	727.0	26.5
0°-60°	1184.1	43.1
0°-90°	1420.0	51.7
90°-120°	649.7	23.7
90°-150°	1167.9	42.5
90°-180°	1327.0	48.3
0°-180°	2747.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	470	470	470	470	470	
5°	470	558	471	417	470	45
15°	448	831	452	340	448	127
25°	410	987	411	300	410	189
35°	362	532	359	276	362	226
45°	300	287	292	234	300	230
55°	213	195	204	186	213	191
65°	132	127	125	131	132	131
75°	63	65	59	70	63	68
85°	14	15	11	14	14	16
90°	1	10	1	10	1	2
95°	12	41	12	41	12	13
105°	41	454	41	454	41	44
115°	73	552	73	552	73	72
125°	102	436	102	436	102	90
135°	119	353	119	353	119	92
145°	136	276	136	276	136	85
155°	155	229	155	229	155	71
165°	169	200	169	200	169	48
175°	176	180	176	180	176	17
180°	176	176	176	176	176	

TEST NUMBER: P1011567

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	471.5	475.2	477.0	479.7	482.5	486.6	487.9	490.2	489.3	491.1	492.0
5°	469.7	476.1	481.5	488.4	494.8	499.3	503.9	511.2	516.6	517.5	521.6
7.5°	466.5	475.6	485.2	494.8	507.1	514.3	522.5	532.6	540.8	554.0	559.0
10°	462.4	475.2	488.8	502.0	518.9	530.3	540.3	557.2	574.0	587.7	600.4
12.5°	456.0	472.0	489.7	509.3	531.2	544.4	558.1	580.4	605.9	626.9	640.5
15°	448.3	468.3	491.1	512.1	536.2	560.8	575.4	600.4	636.9	656.5	691.6
17.5°	441.9	462.4	485.2	518.0	550.8	575.4	585.9	631.9	656.9	689.7	729.4
20°	431.9	457.9	487.0	519.8	562.2	577.2	598.6	645.1	676.1	718.9	767.6
22.5°	421.4	449.2	484.3	518.4	565.8	581.8	610.9	647.8	697.0	739.4	793.2
25°	410.0	440.1	475.6	516.2	562.6	585.9	613.2	658.8	712.1	765.4	815.0
27.5°	398.6	431.4	468.3	508.9	554.0	581.3	608.6	656.0	724.4	782.2	845.5
30°	387.7	420.5	457.4	498.9	546.2	572.7	598.6	657.9	733.9	799.1	862.9
32.5°	375.8	409.6	448.3	482.9	530.7	559.0	588.1	657.9	739.9	809.1	867.4
35°	361.7	396.4	429.6	464.2	511.6	543.0	575.8	653.3	745.3	812.3	848.3
37.5°	348.1	378.6	407.3	441.0	490.7	524.4	562.2	647.8	742.6	798.6	808.6
40°	332.6	363.1	386.3	417.8	470.2	509.3	547.6	640.5	730.7	766.3	737.1
42.5°	317.5	341.7	361.7	392.3	449.2	487.5	528.9	627.3	707.5	714.8	649.2
45°	300.2	317.5	335.3	369.9	426.4	465.6	511.6	608.2	670.2	649.2	566.3
47.5°	277.9	293.4	313.0	344.9	402.3	442.8	486.6	583.6	615.9	572.2	481.5
50°	256.5	269.7	287.9	318.9	376.8	416.4	462.9	544.9	560.8	492.0	415.0
52.5°	235.1	245.1	262.9	293.8	351.7	390.0	432.3	505.2	496.1	422.3	354.0
55°	212.8	221.4	238.3	268.8	322.5	359.0	399.5	456.5	432.8	362.6	308.0
57.5°	190.9	200.0	217.3	242.8	293.4	328.9	361.3	405.9	370.4	314.3	266.1
60°	171.3	179.0	192.3	217.3	263.3	292.0	321.6	352.2	322.5	268.3	231.4
62.5°	150.8	158.1	170.4	193.2	232.8	258.3	282.0	307.1	274.3	234.6	201.8
65°	131.7	137.6	149.0	169.9	202.3	223.2	242.4	259.7	233.3	196.8	172.2
67.5°	114.3	119.4	128.9	147.6	174.9	190.0	205.5	220.0	197.7	168.6	147.6
70°	95.7	99.8	108.4	122.1	144.0	159.5	170.8	181.8	161.7	138.5	124.4
72.5°	79.3	83.4	88.8	103.0	118.0	127.6	139.9	145.8	134.4	115.3	101.1
75°	63.3	66.5	71.5	80.6	94.8	101.1	108.9	113.4	103.0	90.2	81.5
77.5°	49.7	51.0	54.7	61.0	70.6	77.9	83.8	86.6	79.3	71.1	63.8
80°	35.1	36.9	39.6	45.1	52.4	54.7	58.3	61.5	56.9	49.7	45.1
82.5°	23.2	25.5	26.9	29.2	33.7	36.4	37.4	40.1	36.0	33.3	31.4
85°	13.7	14.6	15.0	16.4	18.7	20.0	21.4	21.9	21.0	20.5	18.7
87.5°	6.8	6.8	6.8	7.7	8.2	9.1	9.6	9.6	9.6	9.1	8.7
90°	0.7	1.4	2.1	3.2	3.9	4.2	4.6	5.7	6.8	7.9	8.9
92.5°	5.4	7.9	11.4	14.6	18.2	21.4	24.6	36.1	55.0	73.6	66.4
95°	12.1	13.2	17.1	23.2	32.5	39.4	46.4	76.8	130.0	188.6	211.8
97.5°	19.3	19.6	22.9	28.2	37.5	45.2	52.9	82.9	144.6	243.2	325.7
100°	26.4	26.8	29.3	34.3	42.9	49.8	56.8	81.8	134.6	228.6	338.2
102.5°	33.9	34.6	36.8	41.4	48.9	55.2	61.4	83.2	126.1	207.1	315.0
105°	41.4	42.5	44.6	48.9	55.7	61.2	66.8	86.1	122.8	190.3	287.1
107.5°	49.3	50.4	52.5	56.8	63.2	68.4	73.6	90.7	122.1	178.2	262.5
110°	57.9	58.9	60.7	64.6	70.7	75.7	80.7	96.8	123.9	171.8	242.1

TEST NUMBER: P1011567

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	65.7	66.8	68.6	72.5	78.6	83.4	88.2	102.9	127.5	168.2	228.6
115°	73.2	74.6	76.8	80.4	86.4	91.2	96.1	109.6	131.4	167.8	219.6
117.5°	80.7	82.5	84.3	87.5	94.3	98.8	103.2	116.8	136.4	168.2	213.6
120°	88.6	89.6	91.4	95.0	101.8	106.2	110.7	123.6	142.1	169.6	209.6
122.5°	95.4	96.4	98.2	102.1	108.6	113.4	118.2	130.7	147.5	172.1	207.1
125°	101.8	102.5	104.6	108.6	115.3	120.2	125.0	137.5	153.2	174.6	205.0
127.5°	106.8	107.8	110.3	114.3	121.8	126.6	131.4	143.6	157.8	177.5	203.9
130°	111.4	112.5	115.7	120.0	127.5	132.3	137.1	148.9	162.5	180.3	202.8
132.5°	115.0	116.4	120.0	125.3	132.8	137.4	142.1	153.6	166.8	182.5	202.5
135°	119.3	120.7	124.6	130.0	137.5	142.3	147.1	158.2	170.3	184.6	202.1
137.5°	123.2	124.6	128.6	134.3	141.8	146.2	150.7	161.4	173.2	186.1	201.4
140°	127.1	128.9	132.5	138.2	145.3	149.8	154.3	164.6	175.3	187.5	201.1
142.5°	131.4	132.8	136.8	141.8	148.9	153.0	157.1	167.1	177.5	188.6	200.3
145°	136.1	137.1	140.3	145.7	151.8	155.9	160.0	169.3	178.9	188.9	199.6
147.5°	140.7	141.4	144.6	149.3	155.3	158.9	162.5	171.1	180.0	188.9	198.6
150°	145.3	145.7	148.6	153.2	158.2	161.4	164.6	172.8	180.3	188.9	197.1
152.5°	150.0	150.0	152.8	156.8	161.1	164.1	167.1	173.9	181.1	187.8	195.3
155°	154.6	154.6	156.8	160.3	164.3	166.8	169.3	175.3	181.1	187.1	193.2
157.5°	158.2	158.6	160.3	163.6	167.1	169.1	171.1	176.1	181.4	186.1	191.4
160°	162.5	162.5	163.9	166.8	169.3	171.0	172.8	177.1	181.4	185.3	189.3
162.5°	165.7	165.7	166.8	168.9	171.1	172.5	173.9	177.5	181.1	183.9	187.1
165°	168.9	168.6	169.3	171.1	172.5	173.8	175.0	177.8	180.3	182.5	185.0
167.5°	171.4	171.1	171.4	172.8	173.9	174.8	175.7	177.8	180.0	181.1	182.8
170°	173.6	172.8	173.2	174.3	175.0	175.4	175.7	177.5	178.9	179.6	180.7
172.5°	175.0	174.6	174.6	175.3	175.7	175.9	176.1	177.5	178.6	178.6	178.9
175°	176.1	175.7	175.3	176.1	176.1	176.2	176.4	177.1	177.8	177.5	177.5
177.5°	176.8	176.4	176.1	176.4	176.4	176.4	176.4	176.8	177.5	176.8	176.4
180°	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4

TEST NUMBER: P1011567

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	495.2	496.1	499.3	501.6	506.1	505.7	505.7	505.2	503.9	506.1	507.5
5°	529.8	537.6	538.5	548.5	549.0	553.1	555.8	553.5	559.0	558.5	554.4
7.5°	572.7	583.1	588.1	597.7	608.6	605.9	616.4	618.2	617.3	621.9	625.0
10°	619.6	637.8	650.6	668.3	672.9	675.6	682.5	688.4	700.2	691.1	697.0
12.5°	673.3	686.6	703.4	731.7	745.8	754.9	758.1	762.2	770.4	765.4	765.8
15°	718.4	736.2	764.9	800.0	804.1	815.5	812.7	837.3	849.2	831.4	841.4
17.5°	765.4	789.1	823.2	853.7	871.1	878.8	886.1	909.8	908.9	906.1	908.4
20°	795.4	834.2	876.5	917.1	922.1	928.0	947.6	957.6	955.8	963.5	968.6
22.5°	837.8	878.8	923.9	950.8	962.2	969.0	984.5	990.9	993.6	995.4	992.2
25°	873.3	917.1	950.3	974.0	980.9	984.5	989.5	991.3	990.0	986.8	989.5
27.5°	897.5	932.6	955.3	966.3	962.6	956.7	947.1	940.8	926.6	919.8	928.0
30°	907.5	923.0	929.8	911.6	893.4	878.8	860.6	826.9	800.4	808.2	797.7
32.5°	891.6	881.5	848.7	801.8	787.7	764.0	712.5	672.9	674.3	653.3	662.0
35°	844.6	799.1	737.1	666.1	647.4	634.6	578.1	569.5	551.2	531.7	537.1
37.5°	761.7	695.2	620.0	567.6	539.9	512.1	480.2	461.0	450.1	441.9	448.3
40°	660.6	579.5	517.5	470.6	446.9	429.2	407.3	388.2	375.8	374.5	376.8
42.5°	561.3	492.9	436.0	391.3	383.6	362.6	348.5	333.5	329.8	323.9	327.1
45°	475.2	419.6	372.7	336.2	327.1	321.6	304.3	294.8	290.7	287.0	292.5
47.5°	412.8	354.4	320.3	298.4	289.3	280.2	270.6	264.2	261.0	261.5	261.0
50°	352.6	309.8	279.7	262.9	257.4	251.0	243.3	239.2	237.8	233.7	236.9
52.5°	303.4	272.4	251.5	235.5	231.4	226.9	220.5	218.2	215.0	214.1	214.1
55°	263.8	239.6	222.8	212.3	207.3	203.6	200.0	197.3	195.0	195.0	195.0
57.5°	232.8	211.8	199.5	190.4	188.6	185.0	180.9	180.9	177.7	177.2	178.6
60°	206.4	187.7	178.1	170.4	167.7	166.7	162.6	162.6	161.7	159.5	161.3
62.5°	179.5	165.8	157.6	151.7	149.0	149.0	145.8	143.5	143.5	144.0	143.1
65°	154.9	144.9	137.6	133.0	131.7	129.8	129.4	127.6	126.2	126.6	126.2
67.5°	133.0	125.3	120.3	116.6	114.3	113.4	112.1	112.1	111.2	111.6	109.3
70°	113.4	105.7	101.6	97.9	97.0	97.0	95.2	95.7	94.8	96.1	95.2
72.5°	93.4	87.5	84.3	82.9	82.0	81.5	80.6	79.7	79.3	80.2	79.7
75°	75.6	70.6	68.3	67.4	66.5	66.5	66.1	65.6	65.1	65.1	65.1
77.5°	58.8	55.6	52.8	53.8	52.4	52.8	51.5	51.5	51.9	51.5	51.5
80°	43.3	41.0	41.0	40.1	38.3	39.2	39.2	37.8	37.4	38.3	36.9
82.5°	28.7	28.2	27.3	26.9	26.0	26.4	26.0	25.5	25.1	26.0	25.1
85°	16.9	16.9	16.4	15.5	16.4	15.9	15.5	15.5	15.0	15.0	15.0
87.5°	8.7	7.7	7.7	7.3	7.7	6.8	7.3	6.8	6.4	6.8	6.4
90°	8.6	8.9	9.3	9.6	10.0	10.4	10.0	10.4	10.7	10.4	10.7
92.5°	49.6	35.4	27.5	23.9	22.6	21.4	20.7	19.3	19.6	18.9	19.6
95°	171.8	128.6	87.1	68.2	61.8	55.4	48.6	45.4	42.9	41.4	42.9
97.5°	336.8	295.3	222.8	175.7	155.4	135.0	111.1	97.5	88.9	85.0	88.9
100°	408.5	421.0	392.1	350.3	325.0	299.6	263.6	237.5	223.6	223.9	223.6
102.5°	412.1	462.8	468.9	448.9	435.2	421.4	395.3	376.0	365.0	354.6	365.0
105°	389.6	464.3	500.0	506.8	502.2	497.5	481.0	467.5	456.0	454.3	456.0
107.5°	357.5	442.8	498.9	526.7	531.6	536.4	534.2	527.8	523.2	519.3	523.2
110°	327.5	409.3	475.0	520.0	532.5	545.0	555.0	557.8	557.1	556.4	557.1

TEST NUMBER: P1011567

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	301.4	376.0	443.5	495.3	512.2	529.2	549.6	560.0	563.5	563.9	563.5
115°	281.4	347.5	409.6	462.1	481.6	501.0	527.8	543.5	550.7	552.5	550.7
117.5°	268.2	325.3	380.3	428.5	448.7	468.9	496.8	514.3	525.0	527.5	525.0
120°	258.2	308.6	356.8	399.6	417.6	435.7	463.9	483.9	492.5	494.6	492.5
122.5°	250.0	295.3	337.8	376.8	393.2	409.6	433.9	451.4	461.0	463.9	461.0
125°	243.2	283.9	322.8	357.1	371.4	385.7	408.5	424.3	433.2	435.7	433.2
127.5°	236.8	273.6	308.9	340.3	353.6	366.8	387.5	401.0	409.3	411.4	409.3
130°	231.8	263.9	296.1	325.0	337.2	349.3	368.2	381.0	388.5	391.4	388.5
132.5°	227.1	255.0	283.9	310.3	321.8	333.2	350.7	363.5	370.0	371.8	370.0
135°	223.2	247.1	272.5	295.7	305.8	316.0	333.5	344.3	350.7	353.2	350.7
137.5°	219.6	239.6	261.1	281.8	290.9	300.0	315.0	326.0	331.4	333.5	331.4
140°	216.4	233.2	251.4	268.6	276.2	283.9	297.5	307.5	313.2	312.8	313.2
142.5°	213.6	227.1	242.1	256.4	262.8	269.3	280.3	288.9	293.9	293.6	293.9
145°	211.1	222.5	234.3	245.7	250.9	256.1	265.0	272.5	275.3	276.1	275.3
147.5°	208.6	218.6	228.2	237.8	241.6	245.3	252.5	257.8	260.7	261.1	260.7
150°	206.1	214.3	222.5	230.0	233.4	236.8	242.1	246.1	248.2	248.2	248.2
152.5°	203.2	210.3	217.1	223.6	226.2	228.9	232.8	236.4	237.5	237.5	237.5
155°	200.3	206.4	212.1	217.5	219.6	221.8	225.0	227.8	228.6	228.9	228.6
157.5°	197.1	202.1	207.1	211.4	213.2	215.0	217.8	220.0	220.7	220.7	220.7
160°	193.9	198.6	202.5	206.1	207.4	208.6	211.1	213.2	213.2	212.8	213.2
162.5°	190.7	194.3	197.5	200.7	201.8	202.8	204.3	206.1	206.1	205.7	206.1
165°	187.8	190.7	192.8	195.3	196.2	197.1	198.6	200.0	199.6	199.6	199.6
167.5°	185.0	187.5	189.3	190.7	191.4	192.1	192.8	193.9	193.6	193.6	193.6
170°	182.5	184.3	185.3	186.8	187.2	187.5	187.8	188.6	188.2	188.2	188.2
172.5°	180.0	181.4	182.1	183.2	183.4	183.6	183.6	184.3	183.6	183.2	183.6
175°	178.2	178.9	179.3	180.0	180.0	180.0	180.0	180.3	180.0	179.6	180.0
177.5°	176.8	177.1	177.5	177.8	177.8	177.8	177.5	177.8	177.1	177.1	177.1
180°	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4

TEST NUMBER: P1011567

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	503.9	505.2	501.6	500.7	500.7	502.5	501.1	488.8	491.1	488.4	487.5
5°	559.4	556.7	553.1	551.2	549.0	542.6	542.1	528.0	525.3	516.2	512.1
7.5°	620.5	618.2	607.3	605.9	605.0	599.1	584.0	569.0	558.1	547.6	537.6
10°	690.2	683.4	678.4	668.3	663.3	655.1	635.5	621.4	602.7	586.8	565.8
12.5°	774.0	766.3	749.4	742.1	735.8	713.0	693.4	677.4	641.0	630.1	604.1
15°	835.5	819.1	817.3	801.4	800.4	775.4	738.0	720.7	692.5	652.4	625.5
17.5°	902.0	887.5	876.1	856.9	854.2	830.5	803.2	760.8	729.8	691.6	657.4
20°	950.8	943.0	923.5	915.7	899.8	879.7	851.5	799.1	761.3	723.0	681.1
22.5°	989.5	981.8	966.3	955.8	946.7	920.7	887.0	842.4	790.4	740.3	697.0
25°	989.1	986.8	980.4	975.4	968.6	949.4	921.2	878.3	820.5	765.4	705.2
27.5°	933.0	939.4	950.3	955.8	954.4	951.7	935.8	899.8	847.8	782.2	714.8
30°	816.4	839.6	860.1	887.5	895.7	915.7	924.8	904.3	862.9	801.8	727.1
32.5°	677.0	710.7	755.3	770.4	796.3	835.1	878.3	886.1	860.1	813.2	734.8
35°	555.3	583.1	617.8	641.5	664.7	727.6	782.2	829.6	838.3	807.3	733.0
37.5°	459.7	479.3	509.8	529.8	551.2	605.0	681.5	743.0	786.3	787.2	728.0
40°	390.4	399.1	425.5	440.1	460.6	507.1	575.4	655.6	718.9	748.1	714.8
42.5°	330.7	342.1	364.0	374.9	388.2	428.7	473.8	549.9	628.2	690.7	690.2
45°	295.2	303.4	313.4	322.5	337.6	361.7	413.2	470.2	545.3	615.9	643.7
47.5°	263.8	271.5	281.5	284.3	294.3	317.1	348.5	398.2	468.3	538.5	590.9
50°	237.4	243.7	250.6	255.6	260.1	278.8	302.5	344.4	400.5	468.3	533.5
52.5°	216.9	221.4	227.3	230.1	234.2	247.8	266.1	297.0	343.0	405.0	468.3
55°	197.7	200.9	204.6	209.1	210.9	221.0	235.1	261.5	295.7	351.2	411.4
57.5°	180.0	181.3	183.6	186.3	188.6	197.3	209.6	227.3	257.4	300.2	357.2
60°	159.9	163.6	164.9	167.7	169.0	175.9	185.4	200.5	223.7	260.6	303.4
62.5°	143.1	145.3	147.6	149.0	152.2	154.4	162.2	175.9	195.0	222.3	261.0
65°	128.0	128.9	130.3	131.7	132.6	135.3	142.6	151.7	166.3	190.4	220.5
67.5°	110.7	111.6	113.4	113.9	114.8	118.4	122.5	130.3	142.6	160.8	185.4
70°	93.8	95.2	96.1	97.0	98.4	99.8	104.3	110.7	120.3	133.0	152.2
72.5°	79.3	80.6	80.6	81.5	81.1	82.9	87.5	92.0	98.4	108.9	125.7
75°	64.7	64.7	65.6	66.1	66.5	68.3	70.2	73.8	78.8	87.0	97.5
77.5°	51.0	50.6	51.5	51.5	51.5	52.8	54.7	56.5	59.7	65.6	73.8
80°	37.4	37.4	38.3	38.7	37.8	38.3	39.2	41.0	43.3	47.4	51.9
82.5°	24.6	26.4	26.0	26.4	26.0	26.9	27.3	27.8	28.7	30.5	33.7
85°	15.0	15.0	15.0	15.5	15.0	15.5	15.5	15.5	15.9	16.9	18.2
87.5°	6.4	6.4	6.4	6.8	6.4	6.4	6.8	6.4	6.8	6.8	7.3
90°	10.4	10.0	10.4	10.0	9.6	9.3	8.9	8.6	8.9	7.9	6.8
92.5°	19.3	20.7	21.4	22.6	23.9	27.5	35.4	49.6	66.4	73.6	55.0
95°	45.4	48.6	55.4	61.8	68.2	87.1	128.6	171.8	211.8	188.6	130.0
97.5°	97.5	111.1	135.0	155.4	175.7	222.8	295.3	336.8	325.7	243.2	144.6
100°	237.5	263.6	299.6	325.0	350.3	392.1	421.0	408.5	338.2	228.6	134.6
102.5°	376.0	395.3	421.4	435.2	448.9	468.9	462.8	412.1	315.0	207.1	126.1
105°	467.5	481.0	497.5	502.2	506.8	500.0	464.3	389.6	287.1	190.3	122.8
107.5°	527.8	534.2	536.4	531.6	526.7	498.9	442.8	357.5	262.5	178.2	122.1
110°	557.8	555.0	545.0	532.5	520.0	475.0	409.3	327.5	242.1	171.8	123.9

TEST NUMBER: P1011567

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	560.0	549.6	529.2	512.2	495.3	443.5	376.0	301.4	228.6	168.2	127.5
115°	543.5	527.8	501.0	481.6	462.1	409.6	347.5	281.4	219.6	167.8	131.4
117.5°	514.3	496.8	468.9	448.7	428.5	380.3	325.3	268.2	213.6	168.2	136.4
120°	483.9	463.9	435.7	417.6	399.6	356.8	308.6	258.2	209.6	169.6	142.1
122.5°	451.4	433.9	409.6	393.2	376.8	337.8	295.3	250.0	207.1	172.1	147.5
125°	424.3	408.5	385.7	371.4	357.1	322.8	283.9	243.2	205.0	174.6	153.2
127.5°	401.0	387.5	366.8	353.6	340.3	308.9	273.6	236.8	203.9	177.5	157.8
130°	381.0	368.2	349.3	337.2	325.0	296.1	263.9	231.8	202.8	180.3	162.5
132.5°	363.5	350.7	333.2	321.8	310.3	283.9	255.0	227.1	202.5	182.5	166.8
135°	344.3	333.5	316.0	305.8	295.7	272.5	247.1	223.2	202.1	184.6	170.3
137.5°	326.0	315.0	300.0	290.9	281.8	261.1	239.6	219.6	201.4	186.1	173.2
140°	307.5	297.5	283.9	276.2	268.6	251.4	233.2	216.4	201.1	187.5	175.3
142.5°	288.9	280.3	269.3	262.8	256.4	242.1	227.1	213.6	200.3	188.6	177.5
145°	272.5	265.0	256.1	250.9	245.7	234.3	222.5	211.1	199.6	188.9	178.9
147.5°	257.8	252.5	245.3	241.6	237.8	228.2	218.6	208.6	198.6	188.9	180.0
150°	246.1	242.1	236.8	233.4	230.0	222.5	214.3	206.1	197.1	188.9	180.3
152.5°	236.4	232.8	228.9	226.2	223.6	217.1	210.3	203.2	195.3	187.8	181.1
155°	227.8	225.0	221.8	219.6	217.5	212.1	206.4	200.3	193.2	187.1	181.1
157.5°	220.0	217.8	215.0	213.2	211.4	207.1	202.1	197.1	191.4	186.1	181.4
160°	213.2	211.1	208.6	207.4	206.1	202.5	198.6	193.9	189.3	185.3	181.4
162.5°	206.1	204.3	202.8	201.8	200.7	197.5	194.3	190.7	187.1	183.9	181.1
165°	200.0	198.6	197.1	196.2	195.3	192.8	190.7	187.8	185.0	182.5	180.3
167.5°	193.9	192.8	192.1	191.4	190.7	189.3	187.5	185.0	182.8	181.1	180.0
170°	188.6	187.8	187.5	187.2	186.8	185.3	184.3	182.5	180.7	179.6	178.9
172.5°	184.3	183.6	183.6	183.4	183.2	182.1	181.4	180.0	178.9	178.6	178.6
175°	180.3	180.0	180.0	180.0	180.0	179.3	178.9	178.2	177.5	177.5	177.8
177.5°	177.8	177.5	177.8	177.8	177.8	177.5	177.1	176.8	176.4	176.8	177.5
180°	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4

TEST NUMBER: P1011567

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	482.9	481.5	481.5	480.6	477.9	472.9	472.4	473.3	470.6	467.9	463.8
5°	506.6	497.9	495.2	492.5	487.0	477.9	474.3	471.1	466.1	460.1	453.8
7.5°	526.6	514.3	510.7	505.7	494.8	482.0	473.8	467.0	460.1	451.9	444.2
10°	551.7	533.9	525.3	518.0	503.0	485.2	472.9	462.9	451.9	441.9	431.9
12.5°	579.9	551.2	548.5	530.7	513.4	487.0	472.0	457.4	442.8	430.5	420.0
15°	603.6	572.2	560.8	549.0	515.7	482.9	468.3	451.9	435.1	421.9	406.4
17.5°	618.7	592.7	568.6	552.6	518.0	488.8	460.6	441.9	424.1	405.9	393.2
20°	636.9	599.1	578.1	556.7	522.5	484.3	456.0	432.8	410.9	394.5	379.0
22.5°	655.1	604.1	586.8	563.5	523.5	479.7	447.8	424.6	399.5	383.1	366.3
25°	653.3	611.4	582.7	563.1	514.3	475.6	438.3	410.9	387.7	366.7	349.9
27.5°	654.7	603.2	574.0	551.2	508.0	469.7	428.2	399.5	375.4	353.5	335.8
30°	655.1	590.9	565.4	538.0	496.1	455.6	416.9	387.7	362.2	338.5	322.5
32.5°	653.8	580.9	549.0	524.4	477.4	441.9	403.6	372.7	346.7	324.8	309.8
35°	650.6	569.0	532.1	501.1	458.3	422.3	391.3	359.4	331.7	311.6	294.3
37.5°	641.9	556.3	514.3	483.8	436.0	399.5	372.2	345.8	318.9	295.2	280.6
40°	635.5	538.9	496.6	463.3	411.8	376.3	353.5	328.5	302.0	280.6	266.5
42.5°	620.9	522.5	478.4	438.7	388.2	351.7	330.3	310.2	287.5	266.5	253.8
45°	597.3	504.8	456.0	415.9	362.2	327.6	308.0	291.6	271.5	251.5	238.7
47.5°	564.0	479.3	432.3	392.3	336.7	301.6	282.0	269.7	253.8	236.9	226.0
50°	528.0	451.5	408.2	368.6	312.1	277.9	258.8	247.4	236.9	221.4	210.9
52.5°	481.1	421.9	380.4	342.6	285.6	252.8	236.0	227.8	216.9	205.9	196.8
55°	435.5	383.6	349.4	313.4	259.7	229.2	212.8	204.1	197.7	188.6	181.3
57.5°	382.7	348.1	316.6	283.8	235.5	207.7	192.3	181.8	177.7	173.6	166.7
60°	333.9	307.5	282.0	254.7	210.5	185.4	170.4	162.2	158.1	155.4	150.8
62.5°	289.3	268.8	246.9	225.1	185.0	162.2	150.8	142.6	139.0	138.5	134.4
65°	246.5	231.9	214.1	192.7	161.3	141.2	130.3	125.3	121.2	121.2	118.0
67.5°	203.6	193.6	179.5	164.5	139.9	121.2	111.2	106.6	104.3	104.3	102.0
70°	169.5	162.6	149.9	136.7	115.3	101.1	93.4	89.3	87.9	88.4	86.6
72.5°	137.6	130.3	119.8	110.2	94.3	83.8	78.4	73.8	71.5	72.0	71.5
75°	106.6	103.0	93.8	86.6	73.8	66.5	61.5	59.2	57.4	57.9	56.9
77.5°	80.2	74.7	69.7	64.7	56.9	51.0	46.9	44.6	43.3	43.3	43.3
80°	54.7	53.8	49.7	46.9	40.5	36.0	32.8	32.3	31.0	31.0	31.0
82.5°	35.5	33.3	31.0	29.2	25.5	22.8	21.4	20.5	20.0	19.6	20.5
85°	19.6	18.2	17.3	15.5	14.1	12.8	11.4	10.9	10.5	10.9	10.5
87.5°	7.7	6.4	6.4	5.9	5.5	5.0	5.0	4.1	4.1	3.6	3.6
90°	5.7	4.6	4.2	3.9	3.2	2.1	1.4	0.7	1.4	2.1	3.2
92.5°	36.1	24.6	21.4	18.2	14.6	11.4	7.9	5.4	7.9	11.4	14.6
95°	76.8	46.4	39.4	32.5	23.2	17.1	13.2	12.1	13.2	17.1	23.2
97.5°	82.9	52.9	45.2	37.5	28.2	22.9	19.6	19.3	19.6	22.9	28.2
100°	81.8	56.8	49.8	42.9	34.3	29.3	26.8	26.4	26.8	29.3	34.3
102.5°	83.2	61.4	55.2	48.9	41.4	36.8	34.6	33.9	34.6	36.8	41.4
105°	86.1	66.8	61.2	55.7	48.9	44.6	42.5	41.4	42.5	44.6	48.9
107.5°	90.7	73.6	68.4	63.2	56.8	52.5	50.4	49.3	50.4	52.5	56.8
110°	96.8	80.7	75.7	70.7	64.6	60.7	58.9	57.9	58.9	60.7	64.6

TEST NUMBER: P1011567

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	102.9	88.2	83.4	78.6	72.5	68.6	66.8	65.7	66.8	68.6	72.5
115°	109.6	96.1	91.2	86.4	80.4	76.8	74.6	73.2	74.6	76.8	80.4
117.5°	116.8	103.2	98.8	94.3	87.5	84.3	82.5	80.7	82.5	84.3	87.5
120°	123.6	110.7	106.2	101.8	95.0	91.4	89.6	88.6	89.6	91.4	95.0
122.5°	130.7	118.2	113.4	108.6	102.1	98.2	96.4	95.4	96.4	98.2	102.1
125°	137.5	125.0	120.2	115.3	108.6	104.6	102.5	101.8	102.5	104.6	108.6
127.5°	143.6	131.4	126.6	121.8	114.3	110.3	107.8	106.8	107.8	110.3	114.3
130°	148.9	137.1	132.3	127.5	120.0	115.7	112.5	111.4	112.5	115.7	120.0
132.5°	153.6	142.1	137.4	132.8	125.3	120.0	116.4	115.0	116.4	120.0	125.3
135°	158.2	147.1	142.3	137.5	130.0	124.6	120.7	119.3	120.7	124.6	130.0
137.5°	161.4	150.7	146.2	141.8	134.3	128.6	124.6	123.2	124.6	128.6	134.3
140°	164.6	154.3	149.8	145.3	138.2	132.5	128.9	127.1	128.9	132.5	138.2
142.5°	167.1	157.1	153.0	148.9	141.8	136.8	132.8	131.4	132.8	136.8	141.8
145°	169.3	160.0	155.9	151.8	145.7	140.3	137.1	136.1	137.1	140.3	145.7
147.5°	171.1	162.5	158.9	155.3	149.3	144.6	141.4	140.7	141.4	144.6	149.3
150°	172.8	164.6	161.4	158.2	153.2	148.6	145.7	145.3	145.7	148.6	153.2
152.5°	173.9	167.1	164.1	161.1	156.8	152.8	150.0	150.0	150.0	152.8	156.8
155°	175.3	169.3	166.8	164.3	160.3	156.8	154.6	154.6	154.6	156.8	160.3
157.5°	176.1	171.1	169.1	167.1	163.6	160.3	158.6	158.2	158.6	160.3	163.6
160°	177.1	172.8	171.0	169.3	166.8	163.9	162.5	162.5	162.5	163.9	166.8
162.5°	177.5	173.9	172.5	171.1	168.9	166.8	165.7	165.7	165.7	166.8	168.9
165°	177.8	175.0	173.8	172.5	171.1	169.3	168.6	168.9	168.6	169.3	171.1
167.5°	177.8	175.7	174.8	173.9	172.8	171.4	171.1	171.4	171.1	171.4	172.8
170°	177.5	175.7	175.4	175.0	174.3	173.2	172.8	173.6	172.8	173.2	174.3
172.5°	177.5	176.1	175.9	175.7	175.3	174.6	174.6	175.0	174.6	174.6	175.3
175°	177.1	176.4	176.2	176.1	176.1	175.3	175.7	176.1	175.7	175.3	176.1
177.5°	176.8	176.4	176.4	176.4	176.4	176.1	176.4	176.8	176.4	176.1	176.4
180°	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4

TEST NUMBER: P1011567

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	462.9	462.4	463.3	460.6	456.0	453.8	447.4	446.0	445.6	446.0	446.5
5°	450.1	449.7	448.3	443.7	438.3	434.2	426.4	426.0	423.2	420.5	421.9
7.5°	437.8	436.0	433.3	427.3	420.0	415.5	409.1	404.6	400.9	398.6	396.8
10°	425.5	422.8	420.0	412.3	403.2	396.4	388.6	385.0	380.9	379.0	377.2
12.5°	409.6	406.8	401.8	392.7	387.2	378.6	370.8	367.2	364.9	361.3	359.0
15°	396.8	391.3	388.6	379.0	367.6	366.7	352.6	351.7	347.1	347.1	343.5
17.5°	382.2	378.1	373.1	363.5	355.3	347.1	339.9	337.1	333.0	332.1	330.3
20°	368.1	362.6	360.8	351.2	342.6	332.6	324.8	322.1	320.3	318.4	319.8
22.5°	353.5	349.0	344.4	335.8	329.4	319.4	314.8	312.1	309.3	308.4	308.9
25°	339.4	335.3	330.7	322.1	315.3	307.1	303.0	301.6	300.2	300.2	299.8
27.5°	325.7	321.6	317.5	309.8	303.0	297.0	293.8	292.5	291.1	292.0	292.9
30°	311.6	308.0	304.3	297.5	292.0	286.6	284.7	283.8	283.4	285.6	285.6
32.5°	298.9	295.7	292.9	286.6	281.1	276.5	275.2	275.6	276.1	277.4	278.4
35°	285.6	283.4	280.6	275.2	270.6	266.5	267.0	267.0	267.9	270.2	272.0
37.5°	273.8	270.6	268.3	263.8	260.1	256.5	257.9	259.2	260.1	262.9	263.8
40°	259.7	258.3	256.5	251.9	248.7	248.3	248.7	249.7	251.5	252.8	254.2
42.5°	248.3	246.5	244.2	240.5	237.8	238.3	238.7	239.6	240.5	242.8	244.2
45°	235.5	234.2	232.3	229.2	226.9	227.3	227.8	227.8	228.7	231.4	232.3
47.5°	221.4	221.9	219.6	216.4	215.0	215.0	215.0	215.9	218.2	219.1	219.6
50°	207.7	206.8	206.4	203.2	202.3	201.8	202.3	202.7	205.9	205.5	206.8
52.5°	193.2	193.2	192.7	190.9	189.5	189.5	188.6	190.9	191.8	192.7	194.1
55°	179.0	177.7	177.2	176.3	174.5	174.0	174.9	177.7	178.6	179.5	180.9
57.5°	163.6	163.6	162.6	161.3	161.3	161.3	161.3	163.1	164.5	165.4	168.1
60°	149.4	147.6	146.2	146.2	146.2	145.8	148.5	148.5	151.3	151.7	152.6
62.5°	132.6	131.7	130.8	131.2	130.8	131.7	132.6	134.4	134.9	136.2	137.6
65°	116.6	116.6	115.7	118.4	116.6	116.6	118.9	118.9	119.8	121.2	123.0
67.5°	101.1	101.6	100.7	100.7	101.6	102.0	102.5	104.3	104.8	106.6	108.9
70°	85.2	86.1	86.6	85.6	86.6	87.5	88.4	88.8	90.7	91.6	92.9
72.5°	71.1	72.0	70.6	71.1	71.5	72.4	72.9	73.8	74.7	77.4	78.4
75°	56.9	56.5	56.0	57.9	56.9	58.8	59.2	59.2	60.1	62.4	63.3
77.5°	43.7	43.7	44.2	43.3	44.6	44.2	44.6	46.0	47.4	47.4	51.0
80°	30.5	31.4	31.4	31.4	31.9	32.3	31.4	33.7	34.2	34.2	35.5
82.5°	19.6	20.0	19.6	20.5	20.5	21.4	21.0	21.4	22.3	23.2	23.7
85°	10.5	10.5	11.4	11.4	10.9	11.4	10.9	11.4	12.3	12.3	12.8
87.5°	3.6	3.6	3.6	3.6	4.1	3.6	4.1	4.1	3.6	3.6	5.0
90°	3.9	4.2	4.6	5.7	6.8	7.9	8.9	8.6	8.9	9.3	9.6
92.5°	18.2	21.4	24.6	36.1	55.0	73.6	66.4	49.6	35.4	27.5	23.9
95°	32.5	39.4	46.4	76.8	130.0	188.6	211.8	171.8	128.6	87.1	68.2
97.5°	37.5	45.2	52.9	82.9	144.6	243.2	325.7	336.8	295.3	222.8	175.7
100°	42.9	49.8	56.8	81.8	134.6	228.6	338.2	408.5	421.0	392.1	350.3
102.5°	48.9	55.2	61.4	83.2	126.1	207.1	315.0	412.1	462.8	468.9	448.9
105°	55.7	61.2	66.8	86.1	122.8	190.3	287.1	389.6	464.3	500.0	506.8
107.5°	63.2	68.4	73.6	90.7	122.1	178.2	262.5	357.5	442.8	498.9	526.7
110°	70.7	75.7	80.7	96.8	123.9	171.8	242.1	327.5	409.3	475.0	520.0

TEST NUMBER: P1011567

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	78.6	83.4	88.2	102.9	127.5	168.2	228.6	301.4	376.0	443.5	495.3
115°	86.4	91.2	96.1	109.6	131.4	167.8	219.6	281.4	347.5	409.6	462.1
117.5°	94.3	98.8	103.2	116.8	136.4	168.2	213.6	268.2	325.3	380.3	428.5
120°	101.8	106.2	110.7	123.6	142.1	169.6	209.6	258.2	308.6	356.8	399.6
122.5°	108.6	113.4	118.2	130.7	147.5	172.1	207.1	250.0	295.3	337.8	376.8
125°	115.3	120.2	125.0	137.5	153.2	174.6	205.0	243.2	283.9	322.8	357.1
127.5°	121.8	126.6	131.4	143.6	157.8	177.5	203.9	236.8	273.6	308.9	340.3
130°	127.5	132.3	137.1	148.9	162.5	180.3	202.8	231.8	263.9	296.1	325.0
132.5°	132.8	137.4	142.1	153.6	166.8	182.5	202.5	227.1	255.0	283.9	310.3
135°	137.5	142.3	147.1	158.2	170.3	184.6	202.1	223.2	247.1	272.5	295.7
137.5°	141.8	146.2	150.7	161.4	173.2	186.1	201.4	219.6	239.6	261.1	281.8
140°	145.3	149.8	154.3	164.6	175.3	187.5	201.1	216.4	233.2	251.4	268.6
142.5°	148.9	153.0	157.1	167.1	177.5	188.6	200.3	213.6	227.1	242.1	256.4
145°	151.8	155.9	160.0	169.3	178.9	188.9	199.6	211.1	222.5	234.3	245.7
147.5°	155.3	158.9	162.5	171.1	180.0	188.9	198.6	208.6	218.6	228.2	237.8
150°	158.2	161.4	164.6	172.8	180.3	188.9	197.1	206.1	214.3	222.5	230.0
152.5°	161.1	164.1	167.1	173.9	181.1	187.8	195.3	203.2	210.3	217.1	223.6
155°	164.3	166.8	169.3	175.3	181.1	187.1	193.2	200.3	206.4	212.1	217.5
157.5°	167.1	169.1	171.1	176.1	181.4	186.1	191.4	197.1	202.1	207.1	211.4
160°	169.3	171.0	172.8	177.1	181.4	185.3	189.3	193.9	198.6	202.5	206.1
162.5°	171.1	172.5	173.9	177.5	181.1	183.9	187.1	190.7	194.3	197.5	200.7
165°	172.5	173.8	175.0	177.8	180.3	182.5	185.0	187.8	190.7	192.8	195.3
167.5°	173.9	174.8	175.7	177.8	180.0	181.1	182.8	185.0	187.5	189.3	190.7
170°	175.0	175.4	175.7	177.5	178.9	179.6	180.7	182.5	184.3	185.3	186.8
172.5°	175.7	175.9	176.1	177.5	178.6	178.6	178.9	180.0	181.4	182.1	183.2
175°	176.1	176.2	176.4	177.1	177.8	177.5	177.5	178.2	178.9	179.3	180.0
177.5°	176.4	176.4	176.4	176.8	177.5	176.8	176.4	176.8	177.1	177.5	177.8
180°	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4

TEST NUMBER: P1011567

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	446.0	446.5	444.6	443.3	446.9	444.6	444.6	445.1	444.2	445.6	445.1
5°	421.0	421.4	418.2	419.1	417.3	416.9	416.4	419.1	418.7	418.2	419.1
7.5°	396.4	396.4	395.0	394.1	394.1	392.7	394.5	394.1	395.0	395.0	396.4
10°	375.8	376.8	374.5	372.2	371.7	372.2	372.2	372.7	373.1	376.3	375.8
12.5°	359.0	357.6	357.2	355.8	353.5	352.6	351.7	356.7	355.3	355.3	355.3
15°	340.3	343.5	343.0	338.9	338.0	339.9	338.9	338.9	343.5	343.0	342.6
17.5°	330.3	329.4	328.5	326.2	326.6	326.2	326.6	326.6	329.4	329.4	329.4
20°	318.9	317.1	317.1	316.2	316.2	314.8	316.6	317.1	318.9	318.9	319.4
22.5°	308.9	307.5	307.5	307.1	308.0	306.1	308.0	308.4	308.4	309.8	309.8
25°	300.2	299.3	299.3	300.2	300.2	300.2	300.2	302.0	300.7	301.1	300.7
27.5°	292.5	292.9	293.4	293.8	293.4	293.8	294.3	295.2	295.7	295.2	294.3
30°	285.2	286.6	287.0	287.0	287.9	288.4	288.8	288.8	289.3	287.9	288.8
32.5°	279.7	279.7	280.6	281.1	282.0	282.5	282.5	283.4	282.9	281.5	282.0
35°	272.0	272.0	273.8	274.7	276.1	275.6	276.1	276.1	276.5	275.6	274.3
37.5°	264.2	265.1	265.1	267.0	267.4	267.9	267.4	268.3	267.9	267.0	266.5
40°	255.1	254.7	255.1	256.5	256.9	256.9	256.9	257.9	257.9	257.9	257.4
42.5°	243.7	245.1	244.6	246.0	245.6	245.6	246.5	247.4	247.8	246.5	246.9
45°	232.8	232.8	233.7	233.7	234.2	234.2	236.0	235.1	236.0	235.1	235.5
47.5°	221.0	221.4	221.4	221.9	222.8	223.7	222.8	223.2	223.2	223.7	222.8
50°	207.7	207.7	208.7	210.0	211.8	210.9	210.5	212.3	210.9	210.9	210.0
52.5°	194.1	195.4	195.9	197.3	198.6	199.1	199.5	198.6	199.1	197.7	198.2
55°	180.9	181.3	183.1	184.5	185.9	185.9	185.4	185.9	186.3	184.5	184.5
57.5°	167.7	169.0	170.8	170.8	172.7	172.7	172.2	172.2	172.7	171.3	170.8
60°	153.5	154.9	157.2	157.2	159.9	160.4	159.5	158.5	158.5	157.2	157.6
62.5°	138.5	139.9	141.2	143.5	145.3	144.4	146.2	144.4	144.9	142.1	142.1
65°	125.3	125.7	128.0	130.3	130.3	131.2	130.3	130.8	129.4	129.4	127.6
67.5°	109.8	109.8	112.1	114.3	116.6	116.6	116.6	115.3	115.3	113.9	113.9
70°	96.1	95.7	97.9	99.3	100.7	101.1	100.2	99.8	98.9	97.5	97.0
72.5°	79.3	80.2	82.5	83.4	85.6	85.2	87.5	84.7	84.7	82.5	82.0
75°	64.2	65.1	67.4	68.8	70.2	70.2	71.5	70.2	68.3	67.4	67.0
77.5°	51.0	50.6	52.4	54.7	55.1	54.7	55.6	55.1	53.3	53.3	52.4
80°	36.4	37.8	39.6	39.2	41.0	40.5	40.5	39.6	39.6	38.3	39.2
82.5°	24.1	25.5	26.0	25.5	26.0	26.9	27.3	26.9	26.9	26.0	26.4
85°	12.8	12.8	13.7	14.1	13.7	13.7	14.1	15.5	14.6	13.7	14.6
87.5°	4.1	3.6	3.6	4.1	3.6	3.6	4.1	4.1	4.6	4.6	4.6
90°	10.0	10.4	10.0	10.4	10.7	10.4	10.7	10.4	10.0	10.4	10.0
92.5°	22.6	21.4	20.7	19.3	19.6	18.9	19.6	19.3	20.7	21.4	22.6
95°	61.8	55.4	48.6	45.4	42.9	41.4	42.9	45.4	48.6	55.4	61.8
97.5°	155.4	135.0	111.1	97.5	88.9	85.0	88.9	97.5	111.1	135.0	155.4
100°	325.0	299.6	263.6	237.5	223.6	223.9	223.6	237.5	263.6	299.6	325.0
102.5°	435.2	421.4	395.3	376.0	365.0	354.6	365.0	376.0	395.3	421.4	435.2
105°	502.2	497.5	481.0	467.5	456.0	454.3	456.0	467.5	481.0	497.5	502.2
107.5°	531.6	536.4	534.2	527.8	523.2	519.3	523.2	527.8	534.2	536.4	531.6
110°	532.5	545.0	555.0	557.8	557.1	556.4	557.1	557.8	555.0	545.0	532.5

TEST NUMBER: P1011567

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	512.2	529.2	549.6	560.0	563.5	563.9	563.5	560.0	549.6	529.2	512.2
115°	481.6	501.0	527.8	543.5	550.7	552.5	550.7	543.5	527.8	501.0	481.6
117.5°	448.7	468.9	496.8	514.3	525.0	527.5	525.0	514.3	496.8	468.9	448.7
120°	417.6	435.7	463.9	483.9	492.5	494.6	492.5	483.9	463.9	435.7	417.6
122.5°	393.2	409.6	433.9	451.4	461.0	463.9	461.0	451.4	433.9	409.6	393.2
125°	371.4	385.7	408.5	424.3	433.2	435.7	433.2	424.3	408.5	385.7	371.4
127.5°	353.6	366.8	387.5	401.0	409.3	411.4	409.3	401.0	387.5	366.8	353.6
130°	337.2	349.3	368.2	381.0	388.5	391.4	388.5	381.0	368.2	349.3	337.2
132.5°	321.8	333.2	350.7	363.5	370.0	371.8	370.0	363.5	350.7	333.2	321.8
135°	305.8	316.0	333.5	344.3	350.7	353.2	350.7	344.3	333.5	316.0	305.8
137.5°	290.9	300.0	315.0	326.0	331.4	333.5	331.4	326.0	315.0	300.0	290.9
140°	276.2	283.9	297.5	307.5	313.2	312.8	313.2	307.5	297.5	283.9	276.2
142.5°	262.8	269.3	280.3	288.9	293.9	293.6	293.9	288.9	280.3	269.3	262.8
145°	250.9	256.1	265.0	272.5	275.3	276.1	275.3	272.5	265.0	256.1	250.9
147.5°	241.6	245.3	252.5	257.8	260.7	261.1	260.7	257.8	252.5	245.3	241.6
150°	233.4	236.8	242.1	246.1	248.2	248.2	248.2	246.1	242.1	236.8	233.4
152.5°	226.2	228.9	232.8	236.4	237.5	237.5	237.5	236.4	232.8	228.9	226.2
155°	219.6	221.8	225.0	227.8	228.6	228.9	228.6	227.8	225.0	221.8	219.6
157.5°	213.2	215.0	217.8	220.0	220.7	220.7	220.7	220.0	217.8	215.0	213.2
160°	207.4	208.6	211.1	213.2	213.2	212.8	213.2	213.2	211.1	208.6	207.4
162.5°	201.8	202.8	204.3	206.1	206.1	205.7	206.1	206.1	204.3	202.8	201.8
165°	196.2	197.1	198.6	200.0	199.6	199.6	199.6	200.0	198.6	197.1	196.2
167.5°	191.4	192.1	192.8	193.9	193.6	193.6	193.6	193.9	192.8	192.1	191.4
170°	187.2	187.5	187.8	188.6	188.2	188.2	188.2	188.6	187.8	187.5	187.2
172.5°	183.4	183.6	183.6	184.3	183.6	183.2	183.6	184.3	183.6	183.6	183.4
175°	180.0	180.0	180.0	180.3	180.0	179.6	180.0	180.3	180.0	180.0	180.0
177.5°	177.8	177.8	177.5	177.8	177.1	177.1	177.1	177.8	177.5	177.8	177.8
180°	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4

TEST NUMBER: P1011567

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	446.5	447.4	447.8	446.0	444.6	446.9	450.1	452.4	454.2	456.5	457.9
5°	420.0	423.2	423.2	424.1	425.5	427.8	433.7	437.8	441.5	444.2	446.5
7.5°	397.7	400.0	401.4	403.6	405.9	409.1	415.9	421.9	427.3	430.5	434.2
10°	377.7	379.5	381.8	383.1	387.2	391.8	400.5	405.5	411.8	416.9	421.4
12.5°	358.5	364.9	366.3	365.8	369.5	374.5	383.1	390.9	397.7	402.7	407.7
15°	344.9	347.1	349.9	349.4	357.2	358.5	365.8	374.9	384.1	387.2	391.8
17.5°	329.8	333.5	336.2	337.6	339.9	344.9	351.7	358.5	370.4	370.8	382.7
20°	318.0	321.6	323.5	325.3	326.6	332.6	338.5	346.2	355.8	360.8	367.2
22.5°	310.2	312.1	313.4	314.8	316.6	319.8	327.1	335.8	342.1	347.6	351.7
25°	301.1	303.0	304.8	305.7	307.1	308.9	314.3	321.2	330.3	333.9	338.0
27.5°	294.8	294.8	295.7	295.7	297.5	299.3	303.4	309.8	317.1	321.6	327.1
30°	287.9	287.5	287.9	287.5	287.0	289.7	293.4	298.9	303.9	309.3	313.0
32.5°	281.1	280.6	280.6	281.1	279.3	280.6	282.5	287.5	292.9	295.7	299.8
35°	273.8	272.9	272.9	272.9	272.0	271.1	272.9	277.4	281.1	284.7	287.9
37.5°	266.5	265.1	265.1	264.2	263.3	262.0	262.0	265.6	270.6	272.0	276.1
40°	256.5	256.5	255.6	255.1	254.2	253.3	251.9	255.1	259.7	261.0	264.2
42.5°	246.5	245.1	244.6	244.6	244.6	243.3	242.4	244.6	247.4	249.7	251.5
45°	235.1	234.2	234.6	234.2	233.3	232.8	232.3	233.3	236.4	237.4	239.6
47.5°	222.8	222.3	222.3	221.9	221.4	221.9	220.0	222.3	223.2	224.1	226.0
50°	210.0	209.6	209.1	208.7	208.7	209.1	208.7	208.7	210.5	211.4	213.2
52.5°	197.3	195.9	195.9	195.4	195.4	194.5	195.4	195.9	196.8	197.7	198.6
55°	183.6	183.6	182.2	182.2	181.3	181.3	181.8	181.3	183.1	184.1	184.1
57.5°	170.4	168.6	169.0	168.1	167.2	166.7	166.7	167.7	168.6	168.6	169.5
60°	156.3	154.4	154.0	152.2	153.1	151.7	152.2	152.2	154.0	153.1	154.0
62.5°	142.1	139.9	138.5	137.6	137.6	138.0	137.1	136.7	137.6	138.5	140.3
65°	127.1	125.7	124.4	123.0	123.0	122.5	123.5	122.1	121.6	122.1	123.0
67.5°	111.6	110.2	108.9	107.5	108.0	106.6	105.7	107.1	106.1	106.6	107.5
70°	96.6	95.7	92.9	92.0	91.6	92.0	91.6	90.7	92.0	91.6	92.0
72.5°	81.5	80.6	79.3	77.0	77.0	76.5	76.1	76.1	75.6	75.6	75.6
75°	67.0	65.1	63.8	63.3	62.4	62.0	61.5	60.6	61.0	61.5	60.6
77.5°	51.9	49.7	49.2	49.2	47.8	47.8	48.3	47.8	47.4	47.4	47.4
80°	38.3	36.4	36.4	35.5	34.6	34.6	34.6	34.6	34.2	33.7	34.2
82.5°	24.6	24.1	23.7	23.7	24.6	22.8	23.7	23.2	22.8	22.8	22.3
85°	13.7	14.1	13.7	14.1	13.2	13.7	13.7	13.7	13.2	13.7	12.8
87.5°	5.0	5.0	5.0	5.5	5.5	5.5	5.5	5.5	5.9	5.5	5.5
90°	9.6	9.3	8.9	8.6	8.9	7.9	6.8	5.7	4.6	4.2	3.9
92.5°	23.9	27.5	35.4	49.6	66.4	73.6	55.0	36.1	24.6	21.4	18.2
95°	68.2	87.1	128.6	171.8	211.8	188.6	130.0	76.8	46.4	39.4	32.5
97.5°	175.7	222.8	295.3	336.8	325.7	243.2	144.6	82.9	52.9	45.2	37.5
100°	350.3	392.1	421.0	408.5	338.2	228.6	134.6	81.8	56.8	49.8	42.9
102.5°	448.9	468.9	462.8	412.1	315.0	207.1	126.1	83.2	61.4	55.2	48.9
105°	506.8	500.0	464.3	389.6	287.1	190.3	122.8	86.1	66.8	61.2	55.7
107.5°	526.7	498.9	442.8	357.5	262.5	178.2	122.1	90.7	73.6	68.4	63.2
110°	520.0	475.0	409.3	327.5	242.1	171.8	123.9	96.8	80.7	75.7	70.7

TEST NUMBER: P1011567

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	495.3	443.5	376.0	301.4	228.6	168.2	127.5	102.9	88.2	83.4	78.6
115°	462.1	409.6	347.5	281.4	219.6	167.8	131.4	109.6	96.1	91.2	86.4
117.5°	428.5	380.3	325.3	268.2	213.6	168.2	136.4	116.8	103.2	98.8	94.3
120°	399.6	356.8	308.6	258.2	209.6	169.6	142.1	123.6	110.7	106.2	101.8
122.5°	376.8	337.8	295.3	250.0	207.1	172.1	147.5	130.7	118.2	113.4	108.6
125°	357.1	322.8	283.9	243.2	205.0	174.6	153.2	137.5	125.0	120.2	115.3
127.5°	340.3	308.9	273.6	236.8	203.9	177.5	157.8	143.6	131.4	126.6	121.8
130°	325.0	296.1	263.9	231.8	202.8	180.3	162.5	148.9	137.1	132.3	127.5
132.5°	310.3	283.9	255.0	227.1	202.5	182.5	166.8	153.6	142.1	137.4	132.8
135°	295.7	272.5	247.1	223.2	202.1	184.6	170.3	158.2	147.1	142.3	137.5
137.5°	281.8	261.1	239.6	219.6	201.4	186.1	173.2	161.4	150.7	146.2	141.8
140°	268.6	251.4	233.2	216.4	201.1	187.5	175.3	164.6	154.3	149.8	145.3
142.5°	256.4	242.1	227.1	213.6	200.3	188.6	177.5	167.1	157.1	153.0	148.9
145°	245.7	234.3	222.5	211.1	199.6	188.9	178.9	169.3	160.0	155.9	151.8
147.5°	237.8	228.2	218.6	208.6	198.6	188.9	180.0	171.1	162.5	158.9	155.3
150°	230.0	222.5	214.3	206.1	197.1	188.9	180.3	172.8	164.6	161.4	158.2
152.5°	223.6	217.1	210.3	203.2	195.3	187.8	181.1	173.9	167.1	164.1	161.1
155°	217.5	212.1	206.4	200.3	193.2	187.1	181.1	175.3	169.3	166.8	164.3
157.5°	211.4	207.1	202.1	197.1	191.4	186.1	181.4	176.1	171.1	169.1	167.1
160°	206.1	202.5	198.6	193.9	189.3	185.3	181.4	177.1	172.8	171.0	169.3
162.5°	200.7	197.5	194.3	190.7	187.1	183.9	181.1	177.5	173.9	172.5	171.1
165°	195.3	192.8	190.7	187.8	185.0	182.5	180.3	177.8	175.0	173.8	172.5
167.5°	190.7	189.3	187.5	185.0	182.8	181.1	180.0	177.8	175.7	174.8	173.9
170°	186.8	185.3	184.3	182.5	180.7	179.6	178.9	177.5	175.7	175.4	175.0
172.5°	183.2	182.1	181.4	180.0	178.9	178.6	178.6	177.5	176.1	175.9	175.7
175°	180.0	179.3	178.9	178.2	177.5	177.5	177.8	177.1	176.4	176.2	176.1
177.5°	177.8	177.5	177.1	176.8	176.4	176.8	177.5	176.8	176.4	176.4	176.4
180°	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4	176.4

TEST NUMBER: P1011567

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	470.2	470.2	470.2	470.2
2.5°	460.1	461.5	466.1	471.5
5°	451.0	454.7	461.0	469.7
7.5°	441.0	446.5	455.6	466.5
10°	429.6	437.4	448.7	462.4
12.5°	417.3	427.3	441.9	456.0
15°	409.6	419.6	432.8	448.3
17.5°	394.5	406.4	420.0	441.9
20°	379.0	392.3	410.0	431.9
22.5°	367.2	381.3	398.2	421.4
25°	353.1	367.6	385.9	410.0
27.5°	338.0	352.6	373.1	398.6
30°	326.6	340.8	360.4	387.7
32.5°	313.0	326.6	347.1	375.8
35°	297.5	313.0	332.6	361.7
37.5°	285.6	299.8	320.3	348.1
40°	272.9	285.2	305.2	332.6
42.5°	259.2	272.9	290.2	317.5
45°	246.5	256.5	274.3	300.2
47.5°	232.8	244.2	257.9	277.9
50°	218.2	227.8	242.8	256.5
52.5°	204.1	211.8	224.6	235.1
55°	189.1	196.8	206.4	212.8
57.5°	174.9	180.4	186.8	190.9
60°	157.6	163.1	167.2	171.3
62.5°	142.1	146.2	148.5	150.8
65°	126.2	128.5	129.8	131.7
67.5°	108.9	111.2	111.6	114.3
70°	92.9	93.4	94.3	95.7
72.5°	77.9	78.8	78.4	79.3
75°	62.4	63.3	62.4	63.3
77.5°	47.4	48.3	48.3	49.7
80°	34.2	34.6	35.1	35.1
82.5°	22.3	23.7	22.8	23.2
85°	12.8	13.2	13.2	13.7
87.5°	5.9	6.4	5.9	6.8
90°	3.2	2.1	1.4	0.7
92.5°	14.6	11.4	7.9	5.4
95°	23.2	17.1	13.2	12.1
97.5°	28.2	22.9	19.6	19.3
100°	34.3	29.3	26.8	26.4
102.5°	41.4	36.8	34.6	33.9
105°	48.9	44.6	42.5	41.4
107.5°	56.8	52.5	50.4	49.3
110°	64.6	60.7	58.9	57.9

TEST NUMBER: P1011567

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	72.5	68.6	66.8	65.7
115°	80.4	76.8	74.6	73.2
117.5°	87.5	84.3	82.5	80.7
120°	95.0	91.4	89.6	88.6
122.5°	102.1	98.2	96.4	95.4
125°	108.6	104.6	102.5	101.8
127.5°	114.3	110.3	107.8	106.8
130°	120.0	115.7	112.5	111.4
132.5°	125.3	120.0	116.4	115.0
135°	130.0	124.6	120.7	119.3
137.5°	134.3	128.6	124.6	123.2
140°	138.2	132.5	128.9	127.1
142.5°	141.8	136.8	132.8	131.4
145°	145.7	140.3	137.1	136.1
147.5°	149.3	144.6	141.4	140.7
150°	153.2	148.6	145.7	145.3
152.5°	156.8	152.8	150.0	150.0
155°	160.3	156.8	154.6	154.6
157.5°	163.6	160.3	158.6	158.2
160°	166.8	163.9	162.5	162.5
162.5°	168.9	166.8	165.7	165.7
165°	171.1	169.3	168.6	168.9
167.5°	172.8	171.4	171.1	171.4
170°	174.3	173.2	172.8	173.6
172.5°	175.3	174.6	174.6	175.0
175°	176.1	175.3	175.7	176.1
177.5°	176.4	176.1	176.4	176.8
180°	176.4	176.4	176.4	176.4

(END OF REPORT)