

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011714

Luminaire Tested: S123DIP-B560D1025UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011714
REPORT IS A COMBINATION OF REPORTS P989972 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D1025UB50-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5818.0 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011714

CATALOG NUMBER: S123DIP-B560D1025UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1011714

CATALOG NUMBER: S123DIP-B560D1025UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39		
1	96	91	88	84	87	83	80	77	68	66	64	54	53	51	41	40	40	34		
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	37	35	34	28		
3	80	70	63	58	72	64	58	53	53	49	45	42	39	37	33	31	29	24		
4	73	62	55	49	66	57	50	45	47	42	38	38	34	32	29	27	25	21		
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18		
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19	16		
7	57	45	37	32	52	41	34	30	34	29	25	28	24	21	22	19	17	14		
8	53	41	33	28	48	37	31	26	31	26	22	25	22	19	20	17	15	13		
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14	12		
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	13	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8149	8149	8149	8149
5°	8155	9389	8179	7008
10°	8103	11363	8110	6120
15°	7991	13475	8055	5509
20°	7895	15514	7911	5068
25°	7751	15905	7768	4839
30°	7649	13141	7649	4689
35°	7523	8788	7475	4556
40°	7370	6344	7279	4353
45°	7179	5026	6973	4100
50°	6716	4267	6477	3852
55°	6208	3750	5956	3575
60°	5691	3266	5390	3284
65°	5125	2795	4876	2897
70°	4538	2321	4235	2442
75°	3880	1750	3629	1885
80°	3067	1168	2828	1238
85°	2113	536	1691	488

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 13142 cd/sqm

TEST NUMBER: P1011714

CATALOG NUMBER: S123DIP-B560D1025UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.5	1.3
10°-20°	239.1	4.1
20°-30°	402.4	6.9
30°-40°	454.7	7.8
40°-50°	407.3	7.0
50°-60°	328.8	5.7
60°-70°	229.1	3.9
70°-80°	120.2	2.1
80°-90°	31.4	0.5
90°-100°	254.7	4.4
100°-110°	745.6	12.8
110°-120°	728.1	12.5
120°-130°	579.9	10.0
130°-140°	457.5	7.9
140°-150°	341.3	5.9
150°-160°	238.0	4.1
160°-170°	139.8	2.4
170°-180°	45.5	0.8
0°-30°	716.0	12.3
0°-40°	1170.7	20.1
0°-60°	1906.8	32.8
0°-90°	2287.6	39.3
90°-120°	1728.5	29.7
90°-150°	3107.2	53.4
90°-180°	3530.0	60.7
0°-180°	5818.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	757	757	757	757	757	
5°	756	899	759	671	756	72
15°	722	1339	728	547	722	204
25°	660	1589	662	483	660	305
35°	582	856	579	444	582	365
45°	483	462	470	377	483	370
55°	343	314	329	299	343	307
65°	212	204	202	211	212	211
75°	102	105	95	113	102	109
85°	22	24	18	22	22	25
90°	2	28	2	28	2	4
95°	32	110	32	110	32	34
105°	110	1208	110	1208	110	117
115°	195	1470	195	1470	195	193
125°	271	1159	271	1159	271	241
135°	317	940	317	940	317	245
145°	362	734	362	734	362	227
155°	411	609	411	609	411	189
165°	449	531	449	531	449	127
175°	468	478	468	478	468	44
180°	469	469	469	469	469	

TEST NUMBER: P1011714

CATALOG NUMBER: S123DIP-B560D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1
2.5°	759.3	765.2	768.1	772.5	776.9	783.5	785.7	789.4	787.9	790.8	792.3
5°	756.4	766.6	775.4	786.4	796.7	804.0	811.4	823.1	831.9	833.4	840.0
7.5°	751.2	765.9	781.3	796.7	816.5	828.2	841.4	857.6	870.8	892.1	900.1
10°	744.6	765.2	787.2	808.4	835.6	853.9	870.1	897.2	924.3	946.4	966.9
12.5°	734.3	760.0	788.6	820.2	855.4	876.7	898.7	934.6	975.7	1009.4	1031.5
15°	721.9	754.1	790.8	824.6	863.5	903.1	926.5	966.9	1025.6	1057.1	1113.6
17.5°	711.6	744.6	781.3	834.1	886.9	926.5	943.4	1017.5	1057.9	1110.7	1174.5
20°	695.5	737.3	784.2	837.0	905.3	929.5	964.0	1038.8	1088.7	1157.6	1236.1
22.5°	678.6	723.3	779.8	834.8	911.1	936.8	983.8	1043.2	1122.4	1190.6	1277.2
25°	660.2	708.7	765.9	831.2	906.0	943.4	987.4	1060.8	1146.6	1232.5	1312.4
27.5°	641.9	694.7	754.1	819.4	892.1	936.1	980.1	1056.4	1166.4	1259.6	1361.6
30°	624.3	677.1	736.5	803.3	879.6	922.1	964.0	1059.3	1181.8	1286.7	1389.5
32.5°	605.2	659.5	721.9	777.6	854.7	900.1	947.1	1059.3	1191.4	1302.9	1396.8
35°	582.5	638.2	691.8	747.5	823.8	874.5	927.3	1052.0	1200.2	1308.0	1366.0
37.5°	560.5	609.6	655.8	710.1	790.1	844.4	905.3	1043.2	1195.8	1286.0	1302.2
40°	535.5	584.7	622.1	672.7	757.1	820.2	881.8	1031.5	1176.7	1233.9	1187.0
42.5°	511.3	550.2	582.5	631.6	723.3	785.0	851.7	1010.2	1139.3	1151.0	1045.4
45°	483.4	511.3	539.9	595.7	686.7	749.7	823.8	979.4	1079.1	1045.4	911.9
47.5°	447.5	472.4	504.0	555.3	647.8	713.1	783.5	939.8	991.8	921.4	775.4
50°	413.0	434.3	463.6	513.5	606.7	670.5	745.3	877.4	903.1	792.3	668.3
52.5°	378.5	394.7	423.3	473.2	566.3	628.0	696.2	813.6	798.9	680.1	570.0
55°	342.6	356.5	383.7	432.8	519.4	578.1	643.4	735.1	696.9	584.0	495.9
57.5°	307.4	322.1	349.9	391.0	472.4	529.7	581.8	653.6	596.4	506.2	428.4
60°	275.8	288.3	309.6	349.9	424.0	470.2	517.9	567.1	519.4	432.1	372.7
62.5°	242.8	254.6	274.4	311.0	374.9	416.0	454.1	494.5	441.6	377.8	325.0
65°	212.0	221.5	239.9	273.6	325.7	359.5	390.3	418.2	375.6	316.9	277.3
67.5°	184.1	192.2	207.6	237.7	281.7	305.9	330.9	354.3	318.4	271.4	237.7
70°	154.1	160.7	174.6	196.6	231.8	256.8	275.1	292.7	260.4	223.0	200.3
72.5°	127.6	134.3	143.1	165.8	190.0	205.4	225.2	234.8	216.4	185.6	162.9
75°	102.0	107.1	115.2	129.8	152.6	162.9	175.3	182.7	165.8	145.3	131.3
77.5°	80.0	82.2	88.0	98.3	113.7	125.4	135.0	139.4	127.6	114.4	102.7
80°	56.5	59.4	63.8	72.6	84.4	88.0	93.9	99.0	91.7	80.0	72.6
82.5°	37.4	41.1	43.3	47.0	54.3	58.7	60.2	64.6	58.0	53.6	50.6
85°	22.0	23.5	24.2	26.4	30.1	32.3	34.5	35.2	33.7	33.0	30.1
87.5°	11.0	11.0	11.0	12.5	13.2	14.7	15.4	15.4	15.4	14.7	13.9
90°	1.9	3.8	5.7	8.6	10.5	11.4	12.4	15.2	18.1	20.9	23.8
92.5°	14.3	20.9	30.4	39.0	48.5	57.0	65.6	96.0	146.3	195.7	176.7
95°	32.3	35.2	45.6	61.8	86.5	105.0	123.5	204.3	345.8	501.6	563.4
97.5°	51.3	52.3	60.8	75.1	99.8	120.2	140.6	220.4	384.8	647.0	866.5
100°	70.3	71.3	77.9	91.2	114.0	132.6	151.1	217.6	358.2	608.0	899.7
102.5°	90.3	92.2	97.9	110.2	130.2	146.8	163.4	221.4	335.4	551.0	838.0
105°	110.2	113.1	118.8	130.2	148.2	163.0	177.7	229.0	326.8	506.4	763.9
107.5°	131.1	134.0	139.7	151.1	168.2	182.0	195.7	241.3	324.9	474.1	698.3
110°	153.9	156.8	161.5	172.0	188.1	201.4	214.7	257.5	329.7	457.0	644.2

TEST NUMBER: P1011714

CATALOG NUMBER: S123DIP-B560D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	174.8	177.7	182.4	192.9	209.0	221.8	234.7	273.6	339.2	447.5	608.0
115°	194.8	198.6	204.3	213.8	229.9	242.8	255.6	291.7	349.6	446.5	584.3
117.5°	214.7	219.5	224.2	232.8	250.8	262.7	274.6	310.7	362.9	447.5	568.1
120°	235.6	238.5	243.2	252.7	270.8	282.6	294.5	328.7	378.1	451.3	557.7
122.5°	253.7	256.5	261.3	271.7	288.8	301.6	314.5	347.7	392.4	457.9	551.0
125°	270.8	272.7	278.4	288.8	306.9	319.7	332.5	365.8	407.6	464.6	545.3
127.5°	284.1	286.9	293.6	304.0	324.0	336.8	349.6	381.9	419.9	472.2	542.5
130°	296.4	299.3	307.8	319.2	339.2	352.0	364.8	396.2	432.3	479.8	539.6
132.5°	305.9	309.7	319.2	333.5	353.4	365.8	378.1	408.5	443.7	485.5	538.7
135°	317.3	321.1	331.6	345.8	365.8	378.6	391.4	420.9	453.2	491.2	537.7
137.5°	327.8	331.6	342.0	357.2	377.2	389.0	400.9	429.4	460.8	495.0	535.8
140°	338.2	343.0	352.5	367.7	386.7	398.5	410.4	438.0	466.5	498.8	534.9
142.5°	349.6	353.4	363.9	377.2	396.2	407.1	418.0	444.6	472.2	501.6	533.0
145°	362.0	364.8	373.4	387.6	403.8	414.7	425.6	450.3	476.0	502.6	531.1
147.5°	374.3	376.2	384.8	397.1	413.3	422.8	432.3	455.1	478.8	502.6	528.2
150°	386.7	387.6	395.2	407.6	420.9	429.4	438.0	459.8	479.8	502.6	524.4
152.5°	399.0	399.0	406.6	417.1	428.5	436.6	444.6	462.7	481.7	499.7	519.7
155°	411.4	411.4	417.1	426.6	437.0	443.6	450.3	466.5	481.7	497.8	514.0
157.5°	420.9	421.8	426.6	435.1	444.6	449.8	455.1	468.4	482.6	495.0	509.2
160°	432.3	432.3	436.1	443.7	450.3	455.0	459.8	471.2	482.6	493.1	503.5
162.5°	440.8	440.8	443.7	449.4	455.1	458.9	462.7	472.2	481.7	489.3	497.8
165°	449.4	448.4	450.3	455.1	458.9	462.2	465.5	473.1	479.8	485.5	492.1
167.5°	456.0	455.1	456.0	459.8	462.7	465.0	467.4	473.1	478.8	481.7	486.4
170°	461.7	459.8	460.8	463.6	465.5	466.4	467.4	472.2	476.0	477.9	480.7
172.5°	465.5	464.6	464.6	466.5	467.4	467.9	468.4	472.2	475.0	475.0	476.0
175°	468.4	467.4	466.5	468.4	468.4	468.8	469.3	471.2	473.1	472.2	472.2
177.5°	470.3	469.3	468.4	469.3	469.3	469.3	469.3	470.3	472.2	470.3	469.3
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3



TEST NUMBER: P1011714

CATALOG NUMBER: S123DIP-B560D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1
2.5°	797.4	798.9	804.0	807.7	815.0	814.3	814.3	813.6	811.4	815.0	817.2
5°	853.2	865.7	867.1	883.3	884.0	890.6	895.0	891.3	900.1	899.4	892.8
7.5°	922.1	939.0	947.1	962.5	980.1	975.7	992.6	995.5	994.0	1001.4	1006.5
10°	997.7	1027.1	1047.6	1076.2	1083.5	1087.9	1098.9	1108.5	1127.6	1112.9	1122.4
12.5°	1084.3	1105.5	1132.7	1178.2	1200.9	1215.6	1220.7	1227.3	1240.5	1232.5	1233.2
15°	1156.9	1185.5	1231.7	1288.2	1294.8	1313.2	1308.8	1348.4	1367.4	1338.8	1355.0
17.5°	1232.5	1270.6	1325.6	1374.8	1402.7	1415.1	1426.9	1465.0	1463.5	1459.1	1462.8
20°	1280.9	1343.2	1411.5	1476.8	1484.8	1494.4	1525.9	1542.0	1539.1	1551.6	1559.7
22.5°	1349.1	1415.1	1487.8	1531.0	1549.4	1560.4	1585.3	1595.6	1600.0	1602.9	1597.8
25°	1406.3	1476.8	1530.3	1568.5	1579.5	1585.3	1593.4	1596.3	1594.1	1589.0	1593.4
27.5°	1445.2	1501.7	1538.4	1556.0	1550.1	1540.6	1525.2	1514.9	1492.2	1481.2	1494.4
30°	1461.3	1486.3	1497.3	1467.9	1438.6	1415.1	1385.8	1331.5	1288.9	1301.4	1284.5
32.5°	1435.7	1419.5	1366.7	1291.2	1268.4	1230.3	1147.4	1083.5	1085.7	1052.0	1065.9
35°	1360.1	1286.7	1187.0	1072.5	1042.5	1021.9	930.9	917.0	887.7	856.1	864.9
37.5°	1226.6	1119.5	998.4	914.1	869.3	824.6	773.2	742.4	724.8	711.6	721.9
40°	1063.7	933.1	833.4	757.8	719.7	691.1	655.8	625.0	605.2	603.0	606.7
42.5°	903.8	793.8	702.1	630.2	617.7	584.0	561.2	537.0	531.1	521.6	526.7
45°	765.2	675.7	600.1	541.4	526.7	517.9	490.1	474.6	468.0	462.2	471.0
47.5°	664.6	570.7	515.7	480.5	465.8	451.2	435.8	425.5	420.4	421.1	420.4
50°	567.8	498.9	450.4	423.3	414.5	404.2	391.7	385.1	382.9	376.3	381.5
52.5°	488.6	438.7	405.0	379.3	372.7	365.3	355.1	351.4	346.3	344.8	344.8
55°	424.8	385.9	358.7	341.9	333.8	327.9	322.1	317.7	314.0	314.0	314.0
57.5°	374.9	341.1	321.3	306.6	303.7	297.8	291.2	291.2	286.1	285.4	287.6
60°	332.3	302.2	286.8	274.4	270.0	268.5	261.9	261.9	260.4	256.8	259.7
62.5°	289.0	267.0	253.8	244.3	239.9	239.9	234.8	231.1	231.1	231.8	230.4
65°	249.4	233.3	221.5	214.2	212.0	209.1	208.3	205.4	203.2	203.9	203.2
67.5°	214.2	201.7	193.7	187.8	184.1	182.7	180.5	180.5	179.0	179.7	176.1
70°	182.7	170.2	163.6	157.7	156.3	156.3	153.3	154.1	152.6	154.8	153.3
72.5°	150.4	140.9	135.7	133.5	132.0	131.3	129.8	128.4	127.6	129.1	128.4
75°	121.8	113.7	110.0	108.6	107.1	107.1	106.4	105.6	104.9	104.9	104.9
77.5°	94.6	89.5	85.1	86.6	84.4	85.1	82.9	82.9	83.6	82.9	82.9
80°	69.7	66.0	66.0	64.6	61.6	63.1	63.1	60.9	60.2	61.6	59.4
82.5°	46.2	45.5	44.0	43.3	41.8	42.5	41.8	41.1	40.3	41.8	40.3
85°	27.1	27.1	26.4	24.9	26.4	25.7	24.9	24.9	24.2	24.2	24.2
87.5°	13.9	12.5	12.5	11.7	12.5	11.0	11.7	11.0	10.3	11.0	10.3
90°	22.8	23.8	24.7	25.7	26.6	27.6	26.6	27.6	28.5	27.6	28.5
92.5°	132.1	94.1	73.2	63.7	60.4	57.0	55.1	51.3	52.3	50.4	52.3
95°	457.0	342.0	231.8	181.5	164.4	147.3	129.2	120.7	114.0	110.2	114.0
97.5°	895.9	785.7	592.8	467.4	413.2	359.1	295.5	259.4	236.6	226.1	236.6
100°	1086.9	1120.1	1043.2	932.0	864.6	797.1	701.2	631.8	594.7	595.7	594.7
102.5°	1096.4	1231.3	1247.4	1194.2	1157.6	1121.1	1051.7	1000.4	971.0	943.4	971.0
105°	1036.5	1235.1	1330.1	1348.2	1335.8	1323.5	1279.8	1243.6	1213.2	1208.5	1213.2
107.5°	951.0	1178.1	1327.3	1401.4	1414.2	1427.0	1421.3	1404.2	1391.9	1381.4	1391.9
110°	871.2	1088.8	1263.6	1383.3	1416.6	1449.8	1476.4	1484.0	1482.1	1480.2	1482.1

TEST NUMBER: P1011714

CATALOG NUMBER: S123DIP-B560D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	801.9	1000.4	1180.0	1317.8	1362.9	1408.0	1462.2	1489.7	1499.2	1500.2	1499.2
115°	748.7	924.4	1089.7	1229.4	1281.2	1333.0	1404.2	1446.0	1465.0	1469.8	1465.0
117.5°	713.5	865.5	1011.8	1140.1	1193.8	1247.4	1321.6	1368.1	1396.6	1403.3	1396.6
120°	686.9	820.9	949.1	1063.1	1111.1	1159.1	1234.1	1287.4	1310.2	1315.9	1310.2
122.5°	665.1	785.7	898.8	1002.3	1046.0	1089.7	1154.3	1200.9	1226.5	1234.1	1226.5
125°	647.0	755.3	858.9	950.1	988.1	1026.1	1086.9	1128.7	1152.4	1159.1	1152.4
127.5°	629.9	727.8	821.8	905.4	940.6	975.7	1030.8	1066.9	1088.8	1094.5	1088.8
130°	616.6	702.1	787.6	864.6	896.9	929.2	979.5	1013.7	1033.7	1041.3	1033.7
132.5°	604.2	678.4	755.3	825.6	856.0	886.4	933.0	967.2	984.3	989.0	984.3
135°	593.8	657.5	724.9	786.7	813.8	840.8	887.4	915.9	933.0	939.6	933.0
137.5°	584.3	637.5	694.5	749.6	773.8	798.1	838.0	867.4	881.7	887.4	881.7
140°	575.7	620.4	668.9	714.5	734.9	755.3	791.4	818.0	833.2	832.3	833.2
142.5°	568.1	604.2	644.2	682.2	699.3	716.4	745.8	768.6	781.9	781.0	781.9
145°	561.5	591.9	623.2	653.7	667.4	681.2	705.0	724.9	732.5	734.4	732.5
147.5°	554.8	581.4	607.1	632.8	642.8	652.7	671.7	686.0	693.6	694.5	693.6
150°	548.2	570.0	591.9	611.8	620.8	629.9	644.2	654.6	660.3	660.3	660.3
152.5°	540.6	559.6	577.6	594.7	601.8	609.0	619.4	628.9	631.8	631.8	631.8
155°	533.0	549.1	564.3	578.6	584.3	590.0	598.5	606.1	608.0	609.0	608.0
157.5°	524.4	537.7	551.0	562.4	567.2	571.9	579.5	585.2	587.1	587.1	587.1
160°	515.9	528.2	538.7	548.2	551.5	554.8	561.5	567.2	567.2	566.2	567.2
162.5°	507.3	516.8	525.4	533.9	536.8	539.6	543.4	548.2	548.2	547.2	548.2
165°	499.7	507.3	513.0	519.7	522.0	524.4	528.2	532.0	531.1	531.1	531.1
167.5°	492.1	498.8	503.5	507.3	509.2	511.1	513.0	515.9	514.9	514.9	514.9
170°	485.5	490.2	493.1	496.9	497.8	498.8	499.7	501.6	500.7	500.7	500.7
172.5°	478.8	482.6	484.5	487.4	487.8	488.3	488.3	490.2	488.3	487.4	488.3
175°	474.1	476.0	476.9	478.8	478.8	478.8	478.8	479.8	478.8	477.9	478.8
177.5°	470.3	471.2	472.2	473.1	473.1	473.1	472.2	473.1	471.2	471.2	471.2
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1011714

CATALOG NUMBER: S123DIP-B560D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1
2.5°	811.4	813.6	807.7	806.2	806.2	809.2	807.0	787.2	790.8	786.4	785.0
5°	900.9	896.5	890.6	887.7	884.0	873.7	873.0	850.3	845.9	831.2	824.6
7.5°	999.2	995.5	977.9	975.7	974.2	964.7	940.5	916.3	898.7	881.8	865.7
10°	1111.4	1100.4	1092.3	1076.2	1068.1	1054.9	1023.4	1000.6	970.6	944.9	911.1
12.5°	1246.4	1233.9	1206.8	1195.0	1184.8	1148.1	1116.6	1090.9	1032.2	1014.6	972.8
15°	1345.4	1319.0	1316.1	1290.4	1288.9	1248.6	1188.4	1160.6	1115.1	1050.5	1007.2
17.5°	1452.5	1429.1	1410.7	1379.9	1375.5	1337.4	1293.4	1225.1	1175.2	1113.6	1058.6
20°	1531.0	1518.6	1487.0	1474.6	1448.9	1416.6	1371.1	1286.7	1225.9	1164.2	1096.7
22.5°	1593.4	1580.9	1556.0	1539.1	1524.4	1482.6	1428.3	1356.4	1272.8	1192.1	1122.4
25°	1592.7	1589.0	1578.7	1570.7	1559.7	1528.8	1483.4	1414.4	1321.2	1232.5	1135.6
27.5°	1502.4	1512.7	1530.3	1539.1	1536.9	1532.5	1506.8	1448.9	1365.2	1259.6	1151.0
30°	1314.6	1352.0	1385.1	1429.1	1442.3	1474.6	1489.2	1456.2	1389.5	1291.2	1170.8
32.5°	1090.1	1144.4	1216.3	1240.5	1282.3	1344.7	1414.4	1426.9	1385.1	1309.5	1183.3
35°	894.3	939.0	994.8	1032.9	1070.3	1171.6	1259.6	1335.9	1349.8	1300.0	1180.4
37.5°	740.2	771.8	820.9	853.2	887.7	974.2	1097.5	1196.5	1266.2	1267.7	1172.3
40°	628.7	642.6	685.2	708.7	741.7	816.5	926.5	1055.7	1157.6	1204.6	1151.0
42.5°	532.6	550.9	586.2	603.8	625.0	690.3	763.0	885.5	1011.6	1112.1	1111.4
45°	475.4	488.6	504.7	519.4	543.6	582.5	665.4	757.1	878.1	991.8	1036.6
47.5°	424.8	437.2	453.4	457.8	473.9	510.6	561.2	641.2	754.1	867.1	951.5
50°	382.2	392.5	403.5	411.6	418.9	449.0	487.1	554.6	644.8	754.1	859.1
52.5°	349.2	356.5	366.1	370.5	377.1	399.1	428.4	478.3	552.4	652.2	754.1
55°	318.4	323.5	329.4	336.7	339.7	355.8	378.5	421.1	476.1	565.6	662.4
57.5°	289.8	292.0	295.6	300.0	303.7	317.7	337.5	366.1	414.5	483.4	575.1
60°	257.5	263.4	265.6	270.0	272.2	283.2	298.6	322.8	360.2	419.6	488.6
62.5°	230.4	234.0	237.7	239.9	245.0	248.7	261.2	283.2	314.0	358.0	420.4
65°	206.1	207.6	209.8	212.0	213.5	217.9	229.6	244.3	267.8	306.6	355.1
67.5°	178.3	179.7	182.7	183.4	184.9	190.7	197.3	209.8	229.6	259.0	298.6
70°	151.1	153.3	154.8	156.3	158.5	160.7	168.0	178.3	193.7	214.2	245.0
72.5°	127.6	129.8	129.8	131.3	130.6	133.5	140.9	148.2	158.5	175.3	202.5
75°	104.2	104.2	105.6	106.4	107.1	110.0	113.0	118.8	126.9	140.1	157.0
77.5°	82.2	81.4	82.9	82.9	82.9	85.1	88.0	91.0	96.1	105.6	118.8
80°	60.2	60.2	61.6	62.4	60.9	61.6	63.1	66.0	69.7	76.3	83.6
82.5°	39.6	42.5	41.8	42.5	41.8	43.3	44.0	44.8	46.2	49.2	54.3
85°	24.2	24.2	24.2	24.9	24.2	24.9	24.9	24.9	25.7	27.1	29.3
87.5°	10.3	10.3	10.3	11.0	10.3	10.3	11.0	10.3	11.0	11.0	11.7
90°	27.6	26.6	27.6	26.6	25.7	24.7	23.8	22.8	23.8	20.9	18.1
92.5°	51.3	55.1	57.0	60.4	63.7	73.2	94.1	132.1	176.7	195.7	146.3
95°	120.7	129.2	147.3	164.4	181.5	231.8	342.0	457.0	563.4	501.6	345.8
97.5°	259.4	295.5	359.1	413.2	467.4	592.8	785.7	895.9	866.5	647.0	384.8
100°	631.8	701.2	797.1	864.6	932.0	1043.2	1120.1	1086.9	899.7	608.0	358.2
102.5°	1000.4	1051.7	1121.1	1157.6	1194.2	1247.4	1231.3	1096.4	838.0	551.0	335.4
105°	1243.6	1279.8	1323.5	1335.8	1348.2	1330.1	1235.1	1036.5	763.9	506.4	326.8
107.5°	1404.2	1421.3	1427.0	1414.2	1401.4	1327.3	1178.1	951.0	698.3	474.1	324.9
110°	1484.0	1476.4	1449.8	1416.6	1383.3	1263.6	1088.8	871.2	644.2	457.0	329.7

TEST NUMBER: P1011714

CATALOG NUMBER: S123DIP-B560D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1489.7	1462.2	1408.0	1362.9	1317.8	1180.0	1000.4	801.9	608.0	447.5	339.2
115°	1446.0	1404.2	1333.0	1281.2	1229.4	1089.7	924.4	748.7	584.3	446.5	349.6
117.5°	1368.1	1321.6	1247.4	1193.8	1140.1	1011.8	865.5	713.5	568.1	447.5	362.9
120°	1287.4	1234.1	1159.1	1111.1	1063.1	949.1	820.9	686.9	557.7	451.3	378.1
122.5°	1200.9	1154.3	1089.7	1046.0	1002.3	898.8	785.7	665.1	551.0	457.9	392.4
125°	1128.7	1086.9	1026.1	988.1	950.1	858.9	755.3	647.0	545.3	464.6	407.6
127.5°	1066.9	1030.8	975.7	940.6	905.4	821.8	727.8	629.9	542.5	472.2	419.9
130°	1013.7	979.5	929.2	896.9	864.6	787.6	702.1	616.6	539.6	479.8	432.3
132.5°	967.2	933.0	886.4	856.0	825.6	755.3	678.4	604.2	538.7	485.5	443.7
135°	915.9	887.4	840.8	813.8	786.7	724.9	657.5	593.8	537.7	491.2	453.2
137.5°	867.4	838.0	798.1	773.8	749.6	694.5	637.5	584.3	535.8	495.0	460.8
140°	818.0	791.4	755.3	734.9	714.5	668.9	620.4	575.7	534.9	498.8	466.5
142.5°	768.6	745.8	716.4	699.3	682.2	644.2	604.2	568.1	533.0	501.6	472.2
145°	724.9	705.0	681.2	667.4	653.7	623.2	591.9	561.5	531.1	502.6	476.0
147.5°	686.0	671.7	652.7	642.8	632.8	607.1	581.4	554.8	528.2	502.6	478.8
150°	654.6	644.2	629.9	620.8	611.8	591.9	570.0	548.2	524.4	502.6	479.8
152.5°	628.9	619.4	609.0	601.8	594.7	577.6	559.6	540.6	519.7	499.7	481.7
155°	606.1	598.5	590.0	584.3	578.6	564.3	549.1	533.0	514.0	497.8	481.7
157.5°	585.2	579.5	571.9	567.2	562.4	551.0	537.7	524.4	509.2	495.0	482.6
160°	567.2	561.5	554.8	551.5	548.2	538.7	528.2	515.9	503.5	493.1	482.6
162.5°	548.2	543.4	539.6	536.8	533.9	525.4	516.8	507.3	497.8	489.3	481.7
165°	532.0	528.2	524.4	522.0	519.7	513.0	507.3	499.7	492.1	485.5	479.8
167.5°	515.9	513.0	511.1	509.2	507.3	503.5	498.8	492.1	486.4	481.7	478.8
170°	501.6	499.7	498.8	497.8	496.9	493.1	490.2	485.5	480.7	477.9	476.0
172.5°	490.2	488.3	488.3	487.8	487.4	484.5	482.6	478.8	476.0	475.0	475.0
175°	479.8	478.8	478.8	478.8	478.8	476.9	476.0	474.1	472.2	472.2	473.1
177.5°	473.1	472.2	473.1	473.1	473.1	472.2	471.2	470.3	469.3	470.3	472.2
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1011714

CATALOG NUMBER: S123DIP-B560D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1
2.5°	777.6	775.4	775.4	774.0	769.6	761.5	760.8	762.2	757.8	753.4	746.8
5°	815.8	801.8	797.4	793.0	784.2	769.6	763.7	758.6	750.5	740.9	730.7
7.5°	848.1	828.2	822.4	814.3	796.7	776.2	763.0	751.9	740.9	727.7	715.3
10°	888.4	859.8	845.9	834.1	809.9	781.3	761.5	745.3	727.7	711.6	695.5
12.5°	933.9	887.7	883.3	854.7	826.8	784.2	760.0	736.5	713.1	693.3	676.4
15°	972.0	921.4	903.1	884.0	830.4	777.6	754.1	727.7	700.6	679.3	654.4
17.5°	996.2	954.4	915.5	889.9	834.1	787.2	741.7	711.6	683.0	653.6	633.1
20°	1025.6	964.7	930.9	896.5	841.4	779.8	734.3	696.9	661.7	635.3	610.4
22.5°	1054.9	972.8	944.9	907.5	842.9	772.5	721.1	683.7	643.4	617.0	589.8
25°	1052.0	984.5	938.3	906.7	828.2	765.9	705.7	661.7	624.3	590.6	563.4
27.5°	1054.2	971.3	924.3	887.7	818.0	756.4	689.6	643.4	604.5	569.3	540.7
30°	1054.9	951.5	910.4	866.4	798.9	733.6	671.3	624.3	583.2	545.1	519.4
32.5°	1052.7	935.4	884.0	844.4	768.8	711.6	650.0	600.1	558.3	523.1	498.9
35°	1047.6	916.3	856.9	807.0	738.0	680.1	630.2	578.8	534.1	501.8	473.9
37.5°	1033.7	895.7	828.2	779.1	702.1	643.4	599.4	556.8	513.5	475.4	451.9
40°	1023.4	867.9	799.6	746.1	663.2	606.0	569.3	528.9	486.4	451.9	429.2
42.5°	999.9	841.4	770.3	706.5	625.0	566.3	531.9	499.6	462.9	429.2	408.6
45°	961.8	812.8	734.3	669.8	583.2	527.5	495.9	469.5	437.2	405.0	384.4
47.5°	908.2	771.8	696.2	631.6	542.1	485.6	454.1	434.3	408.6	381.5	363.9
50°	850.3	727.0	657.3	593.5	502.5	447.5	416.7	398.3	381.5	356.5	339.7
52.5°	774.7	679.3	612.6	551.7	460.0	407.2	380.0	366.8	349.2	331.6	316.9
55°	701.3	617.7	562.7	504.7	418.2	369.0	342.6	328.7	318.4	303.7	292.0
57.5°	616.2	560.5	509.9	457.0	379.3	334.5	309.6	292.7	286.1	279.5	268.5
60°	537.7	495.2	454.1	410.1	338.9	298.6	274.4	261.2	254.6	250.2	242.8
62.5°	465.8	432.8	397.6	362.4	297.8	261.2	242.8	229.6	223.8	223.0	216.4
65°	396.9	373.4	344.8	310.3	259.7	227.4	209.8	201.7	195.1	195.1	190.0
67.5°	327.9	311.8	289.0	264.8	225.2	195.1	179.0	171.7	168.0	168.0	164.3
70°	272.9	261.9	241.4	220.1	185.6	162.9	150.4	143.8	141.6	142.3	139.4
72.5°	221.5	209.8	192.9	177.5	151.9	135.0	126.2	118.8	115.2	115.9	115.2
75°	171.7	165.8	151.1	139.4	118.8	107.1	99.0	95.4	92.4	93.2	91.7
77.5°	129.1	120.3	112.2	104.2	91.7	82.2	75.6	71.9	69.7	69.7	69.7
80°	88.0	86.6	80.0	75.6	65.3	58.0	52.8	52.1	49.9	49.9	49.9
82.5°	57.2	53.6	49.9	47.0	41.1	36.7	34.5	33.0	32.3	31.5	33.0
85°	31.5	29.3	27.9	24.9	22.7	20.5	18.3	17.6	16.9	17.6	16.9
87.5°	12.5	10.3	10.3	9.5	8.8	8.1	8.1	6.6	6.6	5.9	5.9
90°	15.2	12.4	11.4	10.5	8.6	5.7	3.8	1.9	3.8	5.7	8.6
92.5°	96.0	65.6	57.0	48.5	39.0	30.4	20.9	14.3	20.9	30.4	39.0
95°	204.3	123.5	105.0	86.5	61.8	45.6	35.2	32.3	35.2	45.6	61.8
97.5°	220.4	140.6	120.2	99.8	75.1	60.8	52.3	51.3	52.3	60.8	75.1
100°	217.6	151.1	132.6	114.0	91.2	77.9	71.3	70.3	71.3	77.9	91.2
102.5°	221.4	163.4	146.8	130.2	110.2	97.9	92.2	90.3	92.2	97.9	110.2
105°	229.0	177.7	163.0	148.2	130.2	118.8	113.1	110.2	113.1	118.8	130.2
107.5°	241.3	195.7	182.0	168.2	151.1	139.7	134.0	131.1	134.0	139.7	151.1
110°	257.5	214.7	201.4	188.1	172.0	161.5	156.8	153.9	156.8	161.5	172.0

TEST NUMBER: P1011714

CATALOG NUMBER: S123DIP-B560D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	273.6	234.7	221.8	209.0	192.9	182.4	177.7	174.8	177.7	182.4	192.9
115°	291.7	255.6	242.8	229.9	213.8	204.3	198.6	194.8	198.6	204.3	213.8
117.5°	310.7	274.6	262.7	250.8	232.8	224.2	219.5	214.7	219.5	224.2	232.8
120°	328.7	294.5	282.6	270.8	252.7	243.2	238.5	235.6	238.5	243.2	252.7
122.5°	347.7	314.5	301.6	288.8	271.7	261.3	256.5	253.7	256.5	261.3	271.7
125°	365.8	332.5	319.7	306.9	288.8	278.4	272.7	270.8	272.7	278.4	288.8
127.5°	381.9	349.6	336.8	324.0	304.0	293.6	286.9	284.1	286.9	293.6	304.0
130°	396.2	364.8	352.0	339.2	319.2	307.8	299.3	296.4	299.3	307.8	319.2
132.5°	408.5	378.1	365.8	353.4	333.5	319.2	309.7	305.9	309.7	319.2	333.5
135°	420.9	391.4	378.6	365.8	345.8	331.6	321.1	317.3	321.1	331.6	345.8
137.5°	429.4	400.9	389.0	377.2	357.2	342.0	331.6	327.8	331.6	342.0	357.2
140°	438.0	410.4	398.5	386.7	367.7	352.5	343.0	338.2	343.0	352.5	367.7
142.5°	444.6	418.0	407.1	396.2	377.2	363.9	353.4	349.6	353.4	363.9	377.2
145°	450.3	425.6	414.7	403.8	387.6	373.4	364.8	362.0	364.8	373.4	387.6
147.5°	455.1	432.3	422.8	413.3	397.1	384.8	376.2	374.3	376.2	384.8	397.1
150°	459.8	438.0	429.4	420.9	407.6	395.2	387.6	386.7	387.6	395.2	407.6
152.5°	462.7	444.6	436.6	428.5	417.1	406.6	399.0	399.0	399.0	406.6	417.1
155°	466.5	450.3	443.6	437.0	426.6	417.1	411.4	411.4	411.4	417.1	426.6
157.5°	468.4	455.1	449.8	444.6	435.1	426.6	421.8	420.9	421.8	426.6	435.1
160°	471.2	459.8	455.0	450.3	443.7	436.1	432.3	432.3	432.3	436.1	443.7
162.5°	472.2	462.7	458.9	455.1	449.4	443.7	440.8	440.8	440.8	443.7	449.4
165°	473.1	465.5	462.2	458.9	455.1	450.3	448.4	449.4	448.4	450.3	455.1
167.5°	473.1	467.4	465.0	462.7	459.8	456.0	455.1	456.0	455.1	456.0	459.8
170°	472.2	467.4	466.4	465.5	463.6	460.8	459.8	461.7	459.8	460.8	463.6
172.5°	472.2	468.4	467.9	467.4	466.5	464.6	464.6	465.5	464.6	464.6	466.5
175°	471.2	469.3	468.8	468.4	468.4	466.5	467.4	468.4	467.4	466.5	468.4
177.5°	470.3	469.3	469.3	469.3	469.3	468.4	469.3	470.3	469.3	468.4	469.3
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1011714

CATALOG NUMBER: S123DIP-B560D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1
2.5°	745.3	744.6	746.1	741.7	734.3	730.7	720.4	718.2	717.5	718.2	718.9
5°	724.8	724.1	721.9	714.5	705.7	699.1	686.7	685.9	681.5	677.1	679.3
7.5°	705.0	702.1	697.7	688.1	676.4	669.1	658.8	651.4	645.6	641.9	639.0
10°	685.2	680.8	676.4	663.9	649.2	638.2	625.8	619.9	613.3	610.4	607.4
12.5°	659.5	655.1	647.0	632.4	623.6	609.6	597.2	591.3	587.6	581.8	578.1
15°	639.0	630.2	625.8	610.4	592.0	590.6	567.8	566.3	559.0	559.0	553.1
17.5°	615.5	608.9	600.8	585.4	572.2	559.0	547.3	542.9	536.3	534.8	531.9
20°	592.8	584.0	581.0	565.6	551.7	535.5	523.1	518.7	515.7	512.8	515.0
22.5°	569.3	561.9	554.6	540.7	530.4	514.3	506.9	502.5	498.1	496.7	497.4
25°	546.5	539.9	532.6	518.7	507.7	494.5	487.8	485.6	483.4	483.4	482.7
27.5°	524.5	517.9	511.3	498.9	487.8	478.3	473.2	471.0	468.8	470.2	471.7
30°	501.8	495.9	490.1	479.0	470.2	461.4	458.5	457.0	456.3	460.0	460.0
32.5°	481.2	476.1	471.7	461.4	452.6	445.3	443.1	443.8	444.6	446.8	448.2
35°	460.0	456.3	451.9	443.1	435.8	429.2	429.9	429.9	431.4	435.0	438.0
37.5°	440.9	435.8	432.1	424.8	418.9	413.0	415.2	417.4	418.9	423.3	424.8
40°	418.2	416.0	413.0	405.7	400.6	399.8	400.6	402.0	405.0	407.2	409.4
42.5°	399.8	396.9	393.2	387.3	382.9	383.7	384.4	385.9	387.3	391.0	393.2
45°	379.3	377.1	374.1	369.0	365.3	366.1	366.8	366.8	368.3	372.7	374.1
47.5°	356.5	357.3	353.6	348.5	346.3	346.3	346.3	347.7	351.4	352.9	353.6
50°	334.5	333.1	332.3	327.2	325.7	325.0	325.7	326.5	331.6	330.9	333.1
52.5°	311.0	311.0	310.3	307.4	305.2	305.2	303.7	307.4	308.8	310.3	312.5
55°	288.3	286.1	285.4	283.9	281.0	280.2	281.7	286.1	287.6	289.0	291.2
57.5°	263.4	263.4	261.9	259.7	259.7	259.7	259.7	262.6	264.8	266.3	270.7
60°	240.6	237.7	235.5	235.5	235.5	234.8	239.2	239.2	243.6	244.3	245.8
62.5°	213.5	212.0	210.5	211.3	210.5	212.0	213.5	216.4	217.1	219.3	221.5
65°	187.8	187.8	186.3	190.7	187.8	187.8	191.5	191.5	192.9	195.1	198.1
67.5°	162.9	163.6	162.1	162.1	163.6	164.3	165.1	168.0	168.7	171.7	175.3
70°	137.2	138.7	139.4	137.9	139.4	140.9	142.3	143.1	146.0	147.5	149.7
72.5°	114.4	115.9	113.7	114.4	115.2	116.6	117.4	118.8	120.3	124.7	126.2
75°	91.7	91.0	90.2	93.2	91.7	94.6	95.4	95.4	96.8	100.5	102.0
77.5°	70.4	70.4	71.2	69.7	71.9	71.2	71.9	74.1	76.3	76.3	82.2
80°	49.2	50.6	50.6	50.6	51.4	52.1	50.6	54.3	55.0	55.0	57.2
82.5°	31.5	32.3	31.5	33.0	33.0	34.5	33.7	34.5	35.9	37.4	38.1
85°	16.9	16.9	18.3	18.3	17.6	18.3	17.6	18.3	19.8	19.8	20.5
87.5°	5.9	5.9	5.9	5.9	6.6	5.9	6.6	6.6	5.9	5.9	8.1
90°	10.5	11.4	12.4	15.2	18.1	20.9	23.8	22.8	23.8	24.7	25.7
92.5°	48.5	57.0	65.6	96.0	146.3	195.7	176.7	132.1	94.1	73.2	63.7
95°	86.5	105.0	123.5	204.3	345.8	501.6	563.4	457.0	342.0	231.8	181.5
97.5°	99.8	120.2	140.6	220.4	384.8	647.0	866.5	895.9	785.7	592.8	467.4
100°	114.0	132.6	151.1	217.6	358.2	608.0	899.7	1086.9	1120.1	1043.2	932.0
102.5°	130.2	146.8	163.4	221.4	335.4	551.0	838.0	1096.4	1231.3	1247.4	1194.2
105°	148.2	163.0	177.7	229.0	326.8	506.4	763.9	1036.5	1235.1	1330.1	1348.2
107.5°	168.2	182.0	195.7	241.3	324.9	474.1	698.3	951.0	1178.1	1327.3	1401.4
110°	188.1	201.4	214.7	257.5	329.7	457.0	644.2	871.2	1088.8	1263.6	1383.3

TEST NUMBER: P1011714

CATALOG NUMBER: S123DIP-B560D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	209.0	221.8	234.7	273.6	339.2	447.5	608.0	801.9	1000.4	1180.0	1317.8
115°	229.9	242.8	255.6	291.7	349.6	446.5	584.3	748.7	924.4	1089.7	1229.4
117.5°	250.8	262.7	274.6	310.7	362.9	447.5	568.1	713.5	865.5	1011.8	1140.1
120°	270.8	282.6	294.5	328.7	378.1	451.3	557.7	686.9	820.9	949.1	1063.1
122.5°	288.8	301.6	314.5	347.7	392.4	457.9	551.0	665.1	785.7	898.8	1002.3
125°	306.9	319.7	332.5	365.8	407.6	464.6	545.3	647.0	755.3	858.9	950.1
127.5°	324.0	336.8	349.6	381.9	419.9	472.2	542.5	629.9	727.8	821.8	905.4
130°	339.2	352.0	364.8	396.2	432.3	479.8	539.6	616.6	702.1	787.6	864.6
132.5°	353.4	365.8	378.1	408.5	443.7	485.5	538.7	604.2	678.4	755.3	825.6
135°	365.8	378.6	391.4	420.9	453.2	491.2	537.7	593.8	657.5	724.9	786.7
137.5°	377.2	389.0	400.9	429.4	460.8	495.0	535.8	584.3	637.5	694.5	749.6
140°	386.7	398.5	410.4	438.0	466.5	498.8	534.9	575.7	620.4	668.9	714.5
142.5°	396.2	407.1	418.0	444.6	472.2	501.6	533.0	568.1	604.2	644.2	682.2
145°	403.8	414.7	425.6	450.3	476.0	502.6	531.1	561.5	591.9	623.2	653.7
147.5°	413.3	422.8	432.3	455.1	478.8	502.6	528.2	554.8	581.4	607.1	632.8
150°	420.9	429.4	438.0	459.8	479.8	502.6	524.4	548.2	570.0	591.9	611.8
152.5°	428.5	436.6	444.6	462.7	481.7	499.7	519.7	540.6	559.6	577.6	594.7
155°	437.0	443.6	450.3	466.5	481.7	497.8	514.0	533.0	549.1	564.3	578.6
157.5°	444.6	449.8	455.1	468.4	482.6	495.0	509.2	524.4	537.7	551.0	562.4
160°	450.3	455.0	459.8	471.2	482.6	493.1	503.5	515.9	528.2	538.7	548.2
162.5°	455.1	458.9	462.7	472.2	481.7	489.3	497.8	507.3	516.8	525.4	533.9
165°	458.9	462.2	465.5	473.1	479.8	485.5	492.1	499.7	507.3	513.0	519.7
167.5°	462.7	465.0	467.4	473.1	478.8	481.7	486.4	492.1	498.8	503.5	507.3
170°	465.5	466.4	467.4	472.2	476.0	477.9	480.7	485.5	490.2	493.1	496.9
172.5°	467.4	467.9	468.4	472.2	475.0	475.0	476.0	478.8	482.6	484.5	487.4
175°	468.4	468.8	469.3	471.2	473.1	472.2	472.2	474.1	476.0	476.9	478.8
177.5°	469.3	469.3	469.3	470.3	472.2	470.3	469.3	470.3	471.2	472.2	473.1
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1011714

CATALOG NUMBER: S123DIP-B560D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1
2.5°	718.2	718.9	716.0	713.8	719.7	716.0	716.0	716.7	715.3	717.5	716.7
5°	677.9	678.6	673.5	674.9	672.0	671.3	670.5	674.9	674.2	673.5	674.9
7.5°	638.2	638.2	636.0	634.6	634.6	632.4	635.3	634.6	636.0	636.0	638.2
10°	605.2	606.7	603.0	599.4	598.6	599.4	599.4	600.1	600.8	606.0	605.2
12.5°	578.1	575.9	575.1	572.9	569.3	567.8	566.3	574.4	572.2	572.2	572.2
15°	548.0	553.1	552.4	545.8	544.3	547.3	545.8	545.8	553.1	552.4	551.7
17.5°	531.9	530.4	528.9	525.3	526.0	525.3	526.0	526.0	530.4	530.4	530.4
20°	513.5	510.6	510.6	509.1	509.1	506.9	509.9	510.6	513.5	513.5	514.3
22.5°	497.4	495.2	495.2	494.5	495.9	493.0	495.9	496.7	496.7	498.9	498.9
25°	483.4	482.0	482.0	483.4	483.4	483.4	483.4	486.4	484.2	484.9	484.2
27.5°	471.0	471.7	472.4	473.2	472.4	473.2	473.9	475.4	476.1	475.4	473.9
30°	459.2	461.4	462.2	462.2	463.6	464.4	465.1	465.1	465.8	463.6	465.1
32.5°	450.4	450.4	451.9	452.6	454.1	454.8	454.8	456.3	455.6	453.4	454.1
35°	438.0	438.0	440.9	442.4	444.6	443.8	444.6	444.6	445.3	443.8	441.6
37.5°	425.5	427.0	427.0	429.9	430.6	431.4	430.6	432.1	431.4	429.9	429.2
40°	410.8	410.1	410.8	413.0	413.8	413.8	413.8	415.2	415.2	415.2	414.5
42.5°	392.5	394.7	393.9	396.1	395.4	395.4	396.9	398.3	399.1	396.9	397.6
45°	374.9	374.9	376.3	376.3	377.1	377.1	380.0	378.5	380.0	378.5	379.3
47.5°	355.8	356.5	356.5	357.3	358.7	360.2	358.7	359.5	359.5	360.2	358.7
50°	334.5	334.5	336.0	338.2	341.1	339.7	338.9	341.9	339.7	339.7	338.2
52.5°	312.5	314.7	315.5	317.7	319.9	320.6	321.3	319.9	320.6	318.4	319.1
55°	291.2	292.0	294.9	297.1	299.3	299.3	298.6	299.3	300.0	297.1	297.1
57.5°	270.0	272.2	275.1	275.1	278.0	278.0	277.3	277.3	278.0	275.8	275.1
60°	247.2	249.4	253.1	253.1	257.5	258.2	256.8	255.3	255.3	253.1	253.8
62.5°	223.0	225.2	227.4	231.1	234.0	232.6	235.5	232.6	233.3	228.9	228.9
65°	201.7	202.5	206.1	209.8	209.8	211.3	209.8	210.5	208.3	208.3	205.4
67.5°	176.8	176.8	180.5	184.1	187.8	187.8	187.8	185.6	185.6	183.4	183.4
70°	154.8	154.1	157.7	159.9	162.1	162.9	161.4	160.7	159.2	157.0	156.3
72.5°	127.6	129.1	132.8	134.3	137.9	137.2	140.9	136.5	136.5	132.8	132.0
75°	103.4	104.9	108.6	110.8	113.0	113.0	115.2	113.0	110.0	108.6	107.8
77.5°	82.2	81.4	84.4	88.0	88.8	88.0	89.5	88.8	85.8	85.8	84.4
80°	58.7	60.9	63.8	63.1	66.0	65.3	65.3	63.8	63.8	61.6	63.1
82.5°	38.9	41.1	41.8	41.1	41.8	43.3	44.0	43.3	43.3	41.8	42.5
85°	20.5	20.5	22.0	22.7	22.0	22.0	22.7	24.9	23.5	22.0	23.5
87.5°	6.6	5.9	5.9	6.6	5.9	5.9	6.6	6.6	7.3	7.3	7.3
90°	26.6	27.6	26.6	27.6	28.5	27.6	28.5	27.6	26.6	27.6	26.6
92.5°	60.4	57.0	55.1	51.3	52.3	50.4	52.3	51.3	55.1	57.0	60.4
95°	164.4	147.3	129.2	120.7	114.0	110.2	114.0	120.7	129.2	147.3	164.4
97.5°	413.2	359.1	295.5	259.4	236.6	226.1	236.6	259.4	295.5	359.1	413.2
100°	864.6	797.1	701.2	631.8	594.7	595.7	594.7	631.8	701.2	797.1	864.6
102.5°	1157.6	1121.1	1051.7	1000.4	971.0	943.4	971.0	1000.4	1051.7	1121.1	1157.6
105°	1335.8	1323.5	1279.8	1243.6	1213.2	1208.5	1213.2	1243.6	1279.8	1323.5	1335.8
107.5°	1414.2	1427.0	1421.3	1404.2	1391.9	1381.4	1391.9	1404.2	1421.3	1427.0	1414.2
110°	1416.6	1449.8	1476.4	1484.0	1482.1	1480.2	1482.1	1484.0	1476.4	1449.8	1416.6

TEST NUMBER: P1011714

CATALOG NUMBER: S123DIP-B560D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1362.9	1408.0	1462.2	1489.7	1499.2	1500.2	1499.2	1489.7	1462.2	1408.0	1362.9
115°	1281.2	1333.0	1404.2	1446.0	1465.0	1469.8	1465.0	1446.0	1404.2	1333.0	1281.2
117.5°	1193.8	1247.4	1321.6	1368.1	1396.6	1403.3	1396.6	1368.1	1321.6	1247.4	1193.8
120°	1111.1	1159.1	1234.1	1287.4	1310.2	1315.9	1310.2	1287.4	1234.1	1159.1	1111.1
122.5°	1046.0	1089.7	1154.3	1200.9	1226.5	1234.1	1226.5	1200.9	1154.3	1089.7	1046.0
125°	988.1	1026.1	1086.9	1128.7	1152.4	1159.1	1152.4	1128.7	1086.9	1026.1	988.1
127.5°	940.6	975.7	1030.8	1066.9	1088.8	1094.5	1088.8	1066.9	1030.8	975.7	940.6
130°	896.9	929.2	979.5	1013.7	1033.7	1041.3	1033.7	1013.7	979.5	929.2	896.9
132.5°	856.0	886.4	933.0	967.2	984.3	989.0	984.3	967.2	933.0	886.4	856.0
135°	813.8	840.8	887.4	915.9	933.0	939.6	933.0	915.9	887.4	840.8	813.8
137.5°	773.8	798.1	838.0	867.4	881.7	887.4	881.7	867.4	838.0	798.1	773.8
140°	734.9	755.3	791.4	818.0	833.2	832.3	833.2	818.0	791.4	755.3	734.9
142.5°	699.3	716.4	745.8	768.6	781.9	781.0	781.9	768.6	745.8	716.4	699.3
145°	667.4	681.2	705.0	724.9	732.5	734.4	732.5	724.9	705.0	681.2	667.4
147.5°	642.8	652.7	671.7	686.0	693.6	694.5	693.6	686.0	671.7	652.7	642.8
150°	620.8	629.9	644.2	654.6	660.3	660.3	660.3	654.6	644.2	629.9	620.8
152.5°	601.8	609.0	619.4	628.9	631.8	631.8	631.8	628.9	619.4	609.0	601.8
155°	584.3	590.0	598.5	606.1	608.0	609.0	608.0	606.1	598.5	590.0	584.3
157.5°	567.2	571.9	579.5	585.2	587.1	587.1	587.1	585.2	579.5	571.9	567.2
160°	551.5	554.8	561.5	567.2	567.2	566.2	567.2	567.2	561.5	554.8	551.5
162.5°	536.8	539.6	543.4	548.2	548.2	547.2	548.2	548.2	543.4	539.6	536.8
165°	522.0	524.4	528.2	532.0	531.1	531.1	531.1	532.0	528.2	524.4	522.0
167.5°	509.2	511.1	513.0	515.9	514.9	514.9	514.9	515.9	513.0	511.1	509.2
170°	497.8	498.8	499.7	501.6	500.7	500.7	500.7	501.6	499.7	498.8	497.8
172.5°	487.8	488.3	488.3	490.2	488.3	487.4	488.3	490.2	488.3	488.3	487.8
175°	478.8	478.8	478.8	479.8	478.8	477.9	478.8	479.8	478.8	478.8	478.8
177.5°	473.1	473.1	472.2	473.1	471.2	471.2	471.2	473.1	472.2	473.1	473.1
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1011714

CATALOG NUMBER: S123DIP-B560D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1
2.5°	718.9	720.4	721.1	718.2	716.0	719.7	724.8	728.5	731.4	735.1	737.3
5°	676.4	681.5	681.5	683.0	685.2	688.9	698.4	705.0	710.9	715.3	718.9
7.5°	640.4	644.1	646.3	650.0	653.6	658.8	669.8	679.3	688.1	693.3	699.1
10°	608.2	611.1	614.8	617.0	623.6	630.9	644.8	652.9	663.2	671.3	678.6
12.5°	577.3	587.6	589.8	589.1	595.0	603.0	617.0	629.4	640.4	648.5	656.6
15°	555.3	559.0	563.4	562.7	575.1	577.3	589.1	603.8	618.4	623.6	630.9
17.5°	531.1	537.0	541.4	543.6	547.3	555.3	566.3	577.3	596.4	597.2	616.2
20°	512.1	517.9	520.9	523.8	526.0	535.5	545.1	557.5	572.9	581.0	591.3
22.5°	499.6	502.5	504.7	506.9	509.9	515.0	526.7	540.7	550.9	559.7	566.3
25°	484.9	487.8	490.8	492.3	494.5	497.4	506.2	517.2	531.9	537.7	544.3
27.5°	474.6	474.6	476.1	476.1	479.0	482.0	488.6	498.9	510.6	517.9	526.7
30°	463.6	462.9	463.6	462.9	462.2	466.6	472.4	481.2	489.3	498.1	504.0
32.5°	452.6	451.9	451.9	452.6	449.7	451.9	454.8	462.9	471.7	476.1	482.7
35°	440.9	439.4	439.4	439.4	438.0	436.5	439.4	446.8	452.6	458.5	463.6
37.5°	429.2	427.0	427.0	425.5	424.0	421.8	421.8	427.7	435.8	438.0	444.6
40°	413.0	413.0	411.6	410.8	409.4	407.9	405.7	410.8	418.2	420.4	425.5
42.5°	396.9	394.7	393.9	393.9	393.9	391.7	390.3	393.9	398.3	402.0	405.0
45°	378.5	377.1	377.8	377.1	375.6	374.9	374.1	375.6	380.7	382.2	385.9
47.5°	358.7	358.0	358.0	357.3	356.5	357.3	354.3	358.0	359.5	360.9	363.9
50°	338.2	337.5	336.7	336.0	336.0	336.7	336.0	336.0	338.9	340.4	343.3
52.5°	317.7	315.5	315.5	314.7	314.7	313.3	314.7	315.5	316.9	318.4	319.9
55°	295.6	295.6	293.4	293.4	292.0	292.0	292.7	292.0	294.9	296.4	296.4
57.5°	274.4	271.4	272.2	270.7	269.2	268.5	268.5	270.0	271.4	271.4	272.9
60°	251.6	248.7	248.0	245.0	246.5	244.3	245.0	245.0	248.0	246.5	248.0
62.5°	228.9	225.2	223.0	221.5	221.5	222.3	220.8	220.1	221.5	223.0	226.0
65°	204.7	202.5	200.3	198.1	198.1	197.3	198.8	196.6	195.9	196.6	198.1
67.5°	179.7	177.5	175.3	173.1	173.9	171.7	170.2	172.4	170.9	171.7	173.1
70°	155.5	154.1	149.7	148.2	147.5	148.2	147.5	146.0	148.2	147.5	148.2
72.5°	131.3	129.8	127.6	124.0	124.0	123.2	122.5	122.5	121.8	121.8	121.8
75°	107.8	104.9	102.7	102.0	100.5	99.8	99.0	97.6	98.3	99.0	97.6
77.5°	83.6	80.0	79.2	79.2	77.0	77.0	77.8	77.0	76.3	76.3	76.3
80°	61.6	58.7	58.7	57.2	55.8	55.8	55.8	55.8	55.0	54.3	55.0
82.5°	39.6	38.9	38.1	38.1	39.6	36.7	38.1	37.4	36.7	36.7	35.9
85°	22.0	22.7	22.0	22.7	21.3	22.0	22.0	22.0	21.3	22.0	20.5
87.5°	8.1	8.1	8.1	8.8	8.8	8.8	8.8	8.8	9.5	8.8	8.8
90°	25.7	24.7	23.8	22.8	23.8	20.9	18.1	15.2	12.4	11.4	10.5
92.5°	63.7	73.2	94.1	132.1	176.7	195.7	146.3	96.0	65.6	57.0	48.5
95°	181.5	231.8	342.0	457.0	563.4	501.6	345.8	204.3	123.5	105.0	86.5
97.5°	467.4	592.8	785.7	895.9	866.5	647.0	384.8	220.4	140.6	120.2	99.8
100°	932.0	1043.2	1120.1	1086.9	899.7	608.0	358.2	217.6	151.1	132.6	114.0
102.5°	1194.2	1247.4	1231.3	1096.4	838.0	551.0	335.4	221.4	163.4	146.8	130.2
105°	1348.2	1330.1	1235.1	1036.5	763.9	506.4	326.8	229.0	177.7	163.0	148.2
107.5°	1401.4	1327.3	1178.1	951.0	698.3	474.1	324.9	241.3	195.7	182.0	168.2
110°	1383.3	1263.6	1088.8	871.2	644.2	457.0	329.7	257.5	214.7	201.4	188.1

TEST NUMBER: P1011714

CATALOG NUMBER: S123DIP-B560D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1317.8	1180.0	1000.4	801.9	608.0	447.5	339.2	273.6	234.7	221.8	209.0
115°	1229.4	1089.7	924.4	748.7	584.3	446.5	349.6	291.7	255.6	242.8	229.9
117.5°	1140.1	1011.8	865.5	713.5	568.1	447.5	362.9	310.7	274.6	262.7	250.8
120°	1063.1	949.1	820.9	686.9	557.7	451.3	378.1	328.7	294.5	282.6	270.8
122.5°	1002.3	898.8	785.7	665.1	551.0	457.9	392.4	347.7	314.5	301.6	288.8
125°	950.1	858.9	755.3	647.0	545.3	464.6	407.6	365.8	332.5	319.7	306.9
127.5°	905.4	821.8	727.8	629.9	542.5	472.2	419.9	381.9	349.6	336.8	324.0
130°	864.6	787.6	702.1	616.6	539.6	479.8	432.3	396.2	364.8	352.0	339.2
132.5°	825.6	755.3	678.4	604.2	538.7	485.5	443.7	408.5	378.1	365.8	353.4
135°	786.7	724.9	657.5	593.8	537.7	491.2	453.2	420.9	391.4	378.6	365.8
137.5°	749.6	694.5	637.5	584.3	535.8	495.0	460.8	429.4	400.9	389.0	377.2
140°	714.5	668.9	620.4	575.7	534.9	498.8	466.5	438.0	410.4	398.5	386.7
142.5°	682.2	644.2	604.2	568.1	533.0	501.6	472.2	444.6	418.0	407.1	396.2
145°	653.7	623.2	591.9	561.5	531.1	502.6	476.0	450.3	425.6	414.7	403.8
147.5°	632.8	607.1	581.4	554.8	528.2	502.6	478.8	455.1	432.3	422.8	413.3
150°	611.8	591.9	570.0	548.2	524.4	502.6	479.8	459.8	438.0	429.4	420.9
152.5°	594.7	577.6	559.6	540.6	519.7	499.7	481.7	462.7	444.6	436.6	428.5
155°	578.6	564.3	549.1	533.0	514.0	497.8	481.7	466.5	450.3	443.6	437.0
157.5°	562.4	551.0	537.7	524.4	509.2	495.0	482.6	468.4	455.1	449.8	444.6
160°	548.2	538.7	528.2	515.9	503.5	493.1	482.6	471.2	459.8	455.0	450.3
162.5°	533.9	525.4	516.8	507.3	497.8	489.3	481.7	472.2	462.7	458.9	455.1
165°	519.7	513.0	507.3	499.7	492.1	485.5	479.8	473.1	465.5	462.2	458.9
167.5°	507.3	503.5	498.8	492.1	486.4	481.7	478.8	473.1	467.4	465.0	462.7
170°	496.9	493.1	490.2	485.5	480.7	477.9	476.0	472.2	467.4	466.4	465.5
172.5°	487.4	484.5	482.6	478.8	476.0	475.0	475.0	472.2	468.4	467.9	467.4
175°	478.8	476.9	476.0	474.1	472.2	472.2	473.1	471.2	469.3	468.8	468.4
177.5°	473.1	472.2	471.2	470.3	469.3	470.3	472.2	470.3	469.3	469.3	469.3
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1011714

CATALOG NUMBER: S123DIP-B560D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	757.1	757.1	757.1	757.1
2.5°	740.9	743.1	750.5	759.3
5°	726.3	732.1	742.4	756.4
7.5°	710.1	718.9	733.6	751.2
10°	691.8	704.3	722.6	744.6
12.5°	672.0	688.1	711.6	734.3
15°	659.5	675.7	696.9	721.9
17.5°	635.3	654.4	676.4	711.6
20°	610.4	631.6	660.2	695.5
22.5°	591.3	614.0	641.2	678.6
25°	568.5	592.0	621.4	660.2
27.5°	544.3	567.8	600.8	641.9
30°	526.0	548.7	580.3	624.3
32.5°	504.0	526.0	559.0	605.2
35°	479.0	504.0	535.5	582.5
37.5°	460.0	482.7	515.7	560.5
40°	439.4	459.2	491.5	535.5
42.5°	417.4	439.4	467.3	511.3
45°	396.9	413.0	441.6	483.4
47.5°	374.9	393.2	415.2	447.5
50°	351.4	366.8	391.0	413.0
52.5°	328.7	341.1	361.7	378.5
55°	304.4	316.9	332.3	342.6
57.5°	281.7	290.5	300.8	307.4
60°	253.8	262.6	269.2	275.8
62.5°	228.9	235.5	239.2	242.8
65°	203.2	206.9	209.1	212.0
67.5°	175.3	179.0	179.7	184.1
70°	149.7	150.4	151.9	154.1
72.5°	125.4	126.9	126.2	127.6
75°	100.5	102.0	100.5	102.0
77.5°	76.3	77.8	77.8	80.0
80°	55.0	55.8	56.5	56.5
82.5°	35.9	38.1	36.7	37.4
85°	20.5	21.3	21.3	22.0
87.5°	9.5	10.3	9.5	11.0
90°	8.6	5.7	3.8	1.9
92.5°	39.0	30.4	20.9	14.3
95°	61.8	45.6	35.2	32.3
97.5°	75.1	60.8	52.3	51.3
100°	91.2	77.9	71.3	70.3
102.5°	110.2	97.9	92.2	90.3
105°	130.2	118.8	113.1	110.2
107.5°	151.1	139.7	134.0	131.1
110°	172.0	161.5	156.8	153.9

TEST NUMBER: P1011714

CATALOG NUMBER: S123DIP-B560D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	192.9	182.4	177.7	174.8
115°	213.8	204.3	198.6	194.8
117.5°	232.8	224.2	219.5	214.7
120°	252.7	243.2	238.5	235.6
122.5°	271.7	261.3	256.5	253.7
125°	288.8	278.4	272.7	270.8
127.5°	304.0	293.6	286.9	284.1
130°	319.2	307.8	299.3	296.4
132.5°	333.5	319.2	309.7	305.9
135°	345.8	331.6	321.1	317.3
137.5°	357.2	342.0	331.6	327.8
140°	367.7	352.5	343.0	338.2
142.5°	377.2	363.9	353.4	349.6
145°	387.6	373.4	364.8	362.0
147.5°	397.1	384.8	376.2	374.3
150°	407.6	395.2	387.6	386.7
152.5°	417.1	406.6	399.0	399.0
155°	426.6	417.1	411.4	411.4
157.5°	435.1	426.6	421.8	420.9
160°	443.7	436.1	432.3	432.3
162.5°	449.4	443.7	440.8	440.8
165°	455.1	450.3	448.4	449.4
167.5°	459.8	456.0	455.1	456.0
170°	463.6	460.8	459.8	461.7
172.5°	466.5	464.6	464.6	465.5
175°	468.4	466.5	467.4	468.4
177.5°	469.3	468.4	469.3	470.3
180°	469.3	469.3	469.3	469.3

(END OF REPORT)