

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011812

Luminaire Tested: S123DIP-B560D585UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011812
REPORT IS A COMBINATION OF REPORTS P990101 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D585UB27-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4463.0 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011812

CATALOG NUMBER: S123DIP-B560D585UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1011812

CATALOG NUMBER: S123DIP-B560D585UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	59	59	59
1	99	94	91	87	91	88	84	81	75	73	70	63	62	60	52	51	50	50	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	46	44	43	43	43	38
3	82	73	66	60	76	68	62	57	58	54	50	50	46	43	41	39	37	37	37	33
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	32	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	33	30	28	28	28	25
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	30	27	25	25	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	28	25	28	24	22	22	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	20	20	17
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	24	20	18	18	18	16
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	18	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8402	8402	8402	8402
5°	8408	9682	8432	7225
10°	8354	11716	8363	6310
15°	8239	13894	8307	5680
20°	8140	15996	8157	5226
25°	7992	16400	8010	4990
30°	7887	13549	7887	4835
35°	7756	9061	7707	4697
40°	7600	6542	7506	4488
45°	7403	5181	7189	4227
50°	6926	4400	6678	3971
55°	6400	3866	6141	3686
60°	5868	3366	5557	3387
65°	5284	2883	5028	2986
70°	4676	2393	4367	2517
75°	3998	1805	3739	1944
80°	3160	1204	2915	1276
85°	2180	554	1748	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 13551 cd/sqm

TEST NUMBER: P1011812

CATALOG NUMBER: S123DIP-B560D585UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.8	1.7
10°-20°	246.6	5.5
20°-30°	414.9	9.3
30°-40°	468.9	10.5
40°-50°	419.9	9.4
50°-60°	339.0	7.6
60°-70°	236.2	5.3
70°-80°	124.0	2.8
80°-90°	31.3	0.7
90°-100°	151.9	3.4
100°-110°	444.7	10.0
110°-120°	434.2	9.7
120°-130°	345.8	7.7
130°-140°	272.8	6.1
140°-150°	203.5	4.6
150°-160°	141.9	3.2
160°-170°	83.4	1.9
170°-180°	27.1	0.6
0°-30°	738.2	16.5
0°-40°	1207.1	27.0
0°-60°	1966.1	44.1
0°-90°	2357.5	52.8
90°-120°	1030.8	23.1
90°-150°	1853.0	41.5
90°-180°	2105.0	47.2
0°-180°	4463.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	781	781	781	781	781	
5°	780	927	782	692	780	74
15°	744	1380	750	564	744	210
25°	681	1638	682	498	681	314
35°	601	883	597	458	601	376
45°	498	476	484	389	498	381
55°	353	324	339	309	353	316
65°	219	210	208	218	219	218
75°	105	108	98	116	105	113
85°	23	25	18	23	23	26
90°	1	16	1	16	1	3
95°	19	66	19	66	19	20
105°	66	721	66	721	66	70
115°	116	876	116	876	116	115
125°	162	691	162	691	162	143
135°	189	560	189	560	189	146
145°	216	438	216	438	216	135
155°	245	363	245	363	245	113
165°	268	317	268	317	268	76
175°	279	285	279	285	279	27
180°	280	280	280	280	280	

TEST NUMBER: P1011812

CATALOG NUMBER: S123DIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	782.9	788.9	792.0	796.5	801.0	807.8	810.1	813.9	812.4	815.4	816.9
5°	779.9	790.4	799.5	810.9	821.5	829.0	836.6	848.7	857.8	859.3	866.1
7.5°	774.6	789.7	805.6	821.5	841.9	854.0	867.6	884.2	897.9	919.8	928.1
10°	767.7	788.9	811.6	833.6	861.5	880.5	897.1	925.1	953.1	975.8	996.9
12.5°	757.2	783.6	813.1	845.7	882.0	903.9	926.6	963.7	1006.0	1040.8	1063.5
15°	744.3	777.6	815.4	850.2	890.3	931.1	955.3	996.9	1057.5	1090.0	1148.2
17.5°	733.7	767.7	805.6	860.0	914.5	955.3	972.7	1049.1	1090.7	1145.2	1211.0
20°	717.1	760.2	808.6	863.1	933.4	958.4	993.9	1071.1	1122.5	1193.6	1274.5
22.5°	699.7	745.8	804.1	860.8	939.5	965.9	1014.3	1075.6	1157.3	1227.6	1316.9
25°	680.8	730.7	789.7	857.0	934.2	972.7	1018.1	1093.8	1182.3	1270.8	1353.2
27.5°	661.9	716.3	777.6	844.9	919.8	965.2	1010.6	1089.2	1202.7	1298.7	1403.9
30°	643.7	698.2	759.4	828.3	906.9	950.8	993.9	1092.2	1218.6	1326.7	1432.6
32.5°	624.0	680.0	744.3	801.8	881.2	928.1	976.5	1092.2	1228.4	1343.4	1440.2
35°	600.6	658.1	713.3	770.8	849.4	901.6	956.1	1084.7	1237.5	1348.7	1408.4
37.5°	577.9	628.6	676.2	732.2	814.6	870.6	933.4	1075.6	1232.9	1326.0	1342.6
40°	552.2	602.9	641.4	693.6	780.6	845.7	909.2	1063.5	1213.3	1272.3	1223.9
42.5°	527.2	567.3	600.6	651.3	745.8	809.4	878.2	1041.6	1174.7	1186.8	1077.9
45°	498.5	527.2	556.7	614.2	708.0	773.0	849.4	1009.8	1112.7	1077.9	940.2
47.5°	461.4	487.1	519.6	572.6	667.9	735.2	807.8	969.0	1022.7	950.0	799.5
50°	425.9	447.8	478.0	529.5	625.5	691.4	768.5	904.7	931.1	816.9	689.1
52.5°	390.3	406.9	436.4	487.9	583.9	647.5	717.8	838.9	823.7	701.2	587.7
55°	353.2	367.6	395.6	446.3	535.5	596.0	663.4	757.9	718.6	602.1	511.3
57.5°	316.9	332.1	360.8	403.2	487.1	546.1	599.8	674.0	615.0	521.9	441.7
60°	284.4	297.3	319.2	360.8	437.2	484.9	534.0	584.7	535.5	445.5	384.3
62.5°	250.4	262.5	282.9	320.7	386.5	428.9	468.2	509.8	455.4	389.5	335.1
65°	218.6	228.4	247.3	282.1	335.8	370.6	402.4	431.1	387.3	326.8	285.9
67.5°	189.9	198.2	214.1	245.1	290.5	315.4	341.1	365.3	328.3	279.9	245.1
70°	158.8	165.7	180.0	202.7	239.0	264.7	283.7	301.8	268.5	229.9	206.5
72.5°	131.6	138.4	147.5	170.9	195.9	211.8	232.2	242.0	223.1	191.4	167.9
75°	105.1	110.4	118.8	133.9	157.3	167.9	180.8	188.3	170.9	149.8	135.4
77.5°	82.4	84.7	90.8	101.4	117.2	129.3	139.2	143.7	131.6	118.0	105.9
80°	58.2	61.3	65.8	74.9	87.0	90.8	96.8	102.1	94.6	82.4	74.9
82.5°	38.6	42.4	44.6	48.4	56.0	60.5	62.0	66.6	59.8	55.2	52.2
85°	22.7	24.2	25.0	27.2	31.0	33.3	35.6	36.3	34.8	34.0	31.0
87.5°	11.3	11.3	11.3	12.9	13.6	15.1	15.9	15.9	15.9	15.1	14.4
90°	1.1	2.3	3.4	5.1	6.2	6.8	7.4	9.1	10.8	12.5	14.2
92.5°	8.5	12.5	18.1	23.2	28.9	34.0	39.1	57.2	87.3	116.7	105.4
95°	19.3	21.0	27.2	36.8	51.6	62.6	73.7	121.8	206.2	299.2	336.0
97.5°	30.6	31.2	36.3	44.8	59.5	71.7	83.9	131.5	229.5	385.9	516.7
100°	41.9	42.5	46.5	54.4	68.0	79.0	90.1	129.8	213.6	362.6	536.6
102.5°	53.8	55.0	58.4	65.7	77.6	87.6	97.5	132.0	200.0	328.6	499.7
105°	65.7	67.4	70.8	77.6	88.4	97.2	106.0	136.6	194.9	302.0	455.5
107.5°	78.2	79.9	83.3	90.1	100.3	108.5	116.7	143.9	193.8	282.7	416.5
110°	91.8	93.5	96.3	102.6	112.2	120.2	128.1	153.5	196.6	272.5	384.2



TEST NUMBER: P1011812

CATALOG NUMBER: S123DIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	104.3	106.0	108.8	115.0	124.7	132.4	140.0	163.2	202.3	266.9	362.6
115°	116.2	118.4	121.8	127.5	137.1	144.8	152.4	173.9	208.5	266.3	348.5
117.5°	128.1	130.9	133.7	138.8	149.6	156.6	163.7	185.3	216.4	266.9	338.8
120°	140.5	142.2	145.1	150.7	161.5	168.6	175.6	196.0	225.5	269.1	332.6
122.5°	151.3	153.0	155.8	162.0	172.2	179.8	187.5	207.4	234.0	273.1	328.6
125°	161.5	162.6	166.0	172.2	183.0	190.6	198.3	218.1	243.1	277.1	325.2
127.5°	169.4	171.1	175.1	181.3	193.2	200.8	208.5	227.8	250.4	281.6	323.5
130°	176.8	178.5	183.6	190.4	202.3	210.0	217.6	236.3	257.8	286.1	321.8
132.5°	182.4	184.7	190.4	198.9	210.8	218.2	225.5	243.6	264.6	289.5	321.3
135°	189.2	191.5	197.7	206.2	218.1	225.8	233.4	251.0	270.3	292.9	320.7
137.5°	195.5	197.7	204.0	213.0	224.9	232.0	239.1	256.1	274.8	295.2	319.6
140°	201.7	204.5	210.2	219.3	230.6	237.7	244.8	261.2	278.2	297.5	319.0
142.5°	208.5	210.8	217.0	224.9	236.3	242.8	249.3	265.2	281.6	299.2	317.9
145°	215.9	217.6	222.7	231.2	240.8	247.3	253.8	268.6	283.9	299.7	316.7
147.5°	223.2	224.4	229.5	236.8	246.5	252.2	257.8	271.4	285.6	299.7	315.0
150°	230.6	231.2	235.7	243.1	251.0	256.1	261.2	274.2	286.1	299.7	312.8
152.5°	238.0	238.0	242.5	248.7	255.5	260.4	265.2	275.9	287.3	298.0	309.9
155°	245.3	245.3	248.7	254.4	260.6	264.6	268.6	278.2	287.3	296.9	306.5
157.5°	251.0	251.6	254.4	259.5	265.2	268.3	271.4	279.3	287.8	295.2	303.7
160°	257.8	257.8	260.1	264.6	268.6	271.4	274.2	281.0	287.8	294.1	300.3
162.5°	262.9	262.9	264.6	268.0	271.4	273.6	275.9	281.6	287.3	291.8	296.9
165°	268.0	267.4	268.6	271.4	273.7	275.6	277.6	282.2	286.1	289.5	293.5
167.5°	272.0	271.4	272.0	274.2	275.9	277.4	278.8	282.2	285.6	287.3	290.1
170°	275.4	274.2	274.8	276.5	277.6	278.2	278.8	281.6	283.9	285.0	286.7
172.5°	277.6	277.1	277.1	278.2	278.8	279.0	279.3	281.6	283.3	283.3	283.9
175°	279.3	278.8	278.2	279.3	279.3	279.6	279.9	281.0	282.2	281.6	281.6
177.5°	280.5	279.9	279.3	279.9	279.9	279.9	279.9	280.5	281.6	280.5	279.9
180°	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9

TEST NUMBER: P1011812

CATALOG NUMBER: S123DIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	822.2	823.7	829.0	832.8	840.4	839.6	839.6	838.9	836.6	840.4	842.6
5°	879.7	892.6	894.1	910.7	911.5	918.3	922.8	919.0	928.1	927.4	920.5
7.5°	950.8	968.2	976.5	992.4	1010.6	1006.0	1023.4	1026.4	1024.9	1032.5	1037.8
10°	1028.7	1059.0	1080.1	1109.6	1117.2	1121.7	1133.1	1142.9	1162.6	1147.5	1157.3
12.5°	1118.0	1139.9	1167.9	1214.8	1238.2	1253.4	1258.7	1265.5	1279.1	1270.8	1271.5
15°	1192.8	1222.3	1270.0	1328.2	1335.1	1354.0	1349.4	1390.3	1409.9	1380.4	1397.1
17.5°	1270.8	1310.1	1366.8	1417.5	1446.2	1459.1	1471.2	1510.5	1509.0	1504.5	1508.3
20°	1320.7	1385.0	1455.3	1522.6	1531.0	1540.8	1573.3	1590.0	1586.9	1599.8	1608.1
22.5°	1391.0	1459.1	1534.0	1578.6	1597.5	1608.9	1634.6	1645.2	1649.7	1652.7	1647.4
25°	1450.0	1522.6	1577.9	1617.2	1628.5	1634.6	1642.9	1645.9	1643.7	1638.4	1642.9
27.5°	1490.1	1548.4	1586.2	1604.3	1598.3	1588.4	1572.6	1562.0	1538.5	1527.2	1540.8
30°	1506.8	1532.5	1543.8	1513.6	1483.3	1459.1	1428.8	1372.9	1329.0	1341.9	1324.5
32.5°	1480.3	1463.6	1409.2	1331.3	1307.8	1268.5	1183.0	1117.2	1119.5	1084.7	1099.1
35°	1402.4	1326.7	1223.9	1105.9	1074.8	1053.7	959.9	945.5	915.2	882.7	891.8
37.5°	1264.7	1154.3	1029.5	942.5	896.3	850.2	797.2	765.5	747.3	733.7	744.3
40°	1096.8	962.1	859.3	781.4	742.0	712.5	676.2	644.5	624.0	621.8	625.5
42.5°	931.9	818.4	723.9	649.8	636.9	602.1	578.6	553.7	547.6	537.8	543.1
45°	788.9	696.6	618.7	558.2	543.1	534.0	505.3	489.4	482.6	476.5	485.6
47.5°	685.3	588.5	531.8	495.4	480.3	465.2	449.3	438.7	433.4	434.2	433.4
50°	585.5	514.4	464.4	436.4	427.4	416.8	403.9	397.1	394.8	388.0	393.3
52.5°	503.8	452.3	417.5	391.1	384.3	376.7	366.1	362.3	357.0	355.5	355.5
55°	438.0	397.9	369.9	352.5	344.2	338.1	332.1	327.5	323.7	323.7	323.7
57.5°	386.5	351.7	331.3	316.2	313.2	307.1	300.3	300.3	295.0	294.2	296.5
60°	342.7	311.6	295.8	282.9	278.4	276.8	270.0	270.0	268.5	264.7	267.8
62.5°	298.0	275.3	261.7	251.9	247.3	247.3	242.0	238.3	238.3	239.0	237.5
65°	257.2	240.5	228.4	220.9	218.6	215.6	214.8	211.8	209.5	210.3	209.5
67.5°	220.9	208.0	199.7	193.6	189.9	188.3	186.1	186.1	184.6	185.3	181.5
70°	188.3	175.5	168.7	162.6	161.1	161.1	158.1	158.8	157.3	159.6	158.1
72.5°	155.1	145.2	139.9	137.7	136.2	135.4	133.9	132.4	131.6	133.1	132.4
75°	125.6	117.2	113.5	111.9	110.4	110.4	109.7	108.9	108.2	108.2	108.2
77.5°	97.6	92.3	87.7	89.3	87.0	87.7	85.5	85.5	86.2	85.5	85.5
80°	71.9	68.1	68.1	66.6	63.5	65.1	65.1	62.8	62.0	63.5	61.3
82.5°	47.7	46.9	45.4	44.6	43.1	43.9	43.1	42.4	41.6	43.1	41.6
85°	28.0	28.0	27.2	25.7	27.2	26.5	25.7	25.7	25.0	25.0	25.0
87.5°	14.4	12.9	12.9	12.1	12.9	11.3	12.1	11.3	10.6	11.3	10.6
90°	13.6	14.2	14.7	15.3	15.8	16.4	15.9	16.4	17.0	16.4	17.0
92.5°	78.8	56.1	43.6	38.0	36.0	34.0	32.9	30.6	31.2	30.0	31.2
95°	272.5	204.0	138.3	108.2	98.0	87.8	77.1	72.0	68.0	65.7	68.0
97.5°	534.3	468.6	353.6	278.8	246.5	214.2	176.2	154.7	141.1	134.9	141.1
100°	648.2	668.0	622.1	555.8	515.6	475.4	418.2	376.8	354.7	355.3	354.7
102.5°	653.9	734.3	743.9	712.2	690.4	668.6	627.2	596.6	579.1	562.6	579.1
105°	618.2	736.6	793.2	804.0	796.6	789.3	763.2	741.7	723.6	720.7	723.6
107.5°	567.2	702.6	791.5	835.7	843.4	851.0	847.6	837.4	830.1	823.8	830.1
110°	519.6	649.3	753.6	825.0	844.8	864.6	880.5	885.0	883.9	882.8	883.9

TEST NUMBER: P1011812

CATALOG NUMBER: S123DIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	478.2	596.6	703.7	785.9	812.8	839.7	872.0	888.4	894.1	894.7	894.1
115°	446.5	551.3	649.9	733.2	764.0	794.9	837.4	862.4	873.7	876.5	873.7
117.5°	425.5	516.2	603.4	679.9	711.9	743.9	788.1	815.9	832.9	836.9	832.9
120°	409.7	489.5	566.0	634.0	662.6	691.3	736.0	767.7	781.3	784.7	781.3
122.5°	396.6	468.6	536.0	597.8	623.8	649.9	688.4	716.2	731.5	736.0	731.5
125°	385.9	450.4	512.2	566.6	589.2	611.9	648.2	673.1	687.3	691.3	687.3
127.5°	375.7	434.0	490.1	540.0	561.0	581.9	614.8	636.3	649.3	652.7	649.3
130°	367.7	418.7	469.7	515.6	534.8	554.1	584.2	604.6	616.5	621.0	616.5
132.5°	360.4	404.6	450.4	492.4	510.5	528.6	556.4	576.8	587.0	589.8	587.0
135°	354.1	392.1	432.3	469.1	485.2	501.4	529.2	546.2	556.4	560.4	556.4
137.5°	348.5	380.2	414.2	447.0	461.4	475.9	499.7	517.3	525.8	529.2	525.8
140°	343.4	370.0	398.9	426.1	438.2	450.4	472.0	487.8	496.9	496.3	496.9
142.5°	338.8	360.4	384.2	406.8	417.0	427.2	444.8	458.4	466.3	465.7	466.3
145°	334.9	353.0	371.7	389.8	398.0	406.3	420.4	432.3	436.9	438.0	436.9
147.5°	330.9	346.8	362.1	377.4	383.4	389.3	400.6	409.1	413.6	414.2	413.6
150°	326.9	340.0	353.0	364.9	370.3	375.7	384.2	390.4	393.8	393.8	393.8
152.5°	322.4	333.7	344.5	354.7	359.0	363.2	369.4	375.1	376.8	376.8	376.8
155°	317.9	327.5	336.6	345.1	348.5	351.9	357.0	361.5	362.6	363.2	362.6
157.5°	312.8	320.7	328.6	335.4	338.2	341.1	345.6	349.0	350.2	350.2	350.2
160°	307.7	315.0	321.3	326.9	328.9	330.9	334.9	338.3	338.3	337.7	338.3
162.5°	302.6	308.2	313.3	318.4	320.1	321.8	324.1	326.9	326.9	326.4	326.9
165°	298.0	302.6	306.0	309.9	311.4	312.8	315.0	317.3	316.7	316.7	316.7
167.5°	293.5	297.5	300.3	302.6	303.7	304.8	306.0	307.7	307.1	307.1	307.1
170°	289.5	292.4	294.1	296.3	296.9	297.5	298.0	299.2	298.6	298.6	298.6
172.5°	285.6	287.8	289.0	290.7	291.0	291.2	291.2	292.4	291.2	290.7	291.2
175°	282.7	283.9	284.4	285.6	285.6	285.6	285.6	286.1	285.6	285.0	285.6
177.5°	280.5	281.0	281.6	282.2	282.2	282.2	281.6	282.2	281.0	281.0	281.0
180°	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9

TEST NUMBER: P1011812

CATALOG NUMBER: S123DIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	836.6	838.9	832.8	831.3	831.3	834.3	832.0	811.6	815.4	810.9	809.4
5°	928.9	924.3	918.3	915.2	911.5	900.9	900.1	876.7	872.1	857.0	850.2
7.5°	1030.2	1026.4	1008.3	1006.0	1004.5	994.7	969.7	944.7	926.6	909.2	892.6
10°	1146.0	1134.6	1126.3	1109.6	1101.3	1087.7	1055.2	1031.7	1000.7	974.2	939.5
12.5°	1285.1	1272.3	1244.3	1232.2	1221.6	1183.8	1151.2	1124.8	1064.3	1046.1	1003.0
15°	1387.2	1360.0	1357.0	1330.5	1329.0	1287.4	1225.4	1196.6	1149.7	1083.2	1038.5
17.5°	1497.7	1473.5	1454.6	1422.8	1418.3	1378.9	1333.5	1263.2	1211.8	1148.2	1091.5
20°	1578.6	1565.8	1533.2	1520.4	1493.9	1460.6	1413.7	1326.7	1263.9	1200.4	1130.8
22.5°	1642.9	1630.0	1604.3	1586.9	1571.8	1528.7	1472.7	1398.6	1312.4	1229.2	1157.3
25°	1642.2	1638.4	1627.8	1619.5	1608.1	1576.3	1529.4	1458.3	1362.3	1270.8	1170.9
27.5°	1549.1	1559.7	1577.9	1586.9	1584.7	1580.1	1553.7	1493.9	1407.7	1298.7	1186.8
30°	1355.5	1394.1	1428.1	1473.5	1487.1	1520.4	1535.5	1501.5	1432.6	1331.3	1207.2
32.5°	1124.0	1180.0	1254.1	1279.1	1322.2	1386.5	1458.3	1471.2	1428.1	1350.2	1220.1
35°	922.1	968.2	1025.7	1065.0	1103.6	1208.0	1298.7	1377.4	1391.8	1340.3	1217.1
37.5°	763.2	795.7	846.4	879.7	915.2	1004.5	1131.6	1233.7	1305.6	1307.1	1208.7
40°	648.2	662.6	706.5	730.7	764.7	841.9	955.3	1088.5	1193.6	1242.0	1186.8
42.5°	549.1	568.1	604.4	622.5	644.5	711.8	786.7	913.0	1043.1	1146.7	1146.0
45°	490.1	503.8	520.4	535.5	560.5	600.6	686.1	780.6	905.4	1022.7	1068.8
47.5°	438.0	450.8	467.5	472.0	488.6	526.5	578.6	661.1	777.6	894.1	981.1
50°	394.1	404.7	416.0	424.3	431.9	462.9	502.3	571.8	664.9	777.6	885.7
52.5°	360.0	367.6	377.4	382.0	388.8	411.5	441.7	493.2	569.6	672.4	777.6
55°	328.3	333.6	339.6	347.2	350.2	366.9	390.3	434.2	490.9	583.2	683.0
57.5°	298.8	301.0	304.8	309.4	313.2	327.5	347.9	377.4	427.4	498.5	593.0
60°	265.5	271.5	273.8	278.4	280.6	292.0	307.9	332.8	371.4	432.7	503.8
62.5°	237.5	241.3	245.1	247.3	252.6	256.4	269.3	292.0	323.7	369.1	433.4
65°	212.5	214.1	216.3	218.6	220.1	224.7	236.8	251.9	276.1	316.2	366.1
67.5°	183.8	185.3	188.3	189.1	190.6	196.7	203.5	216.3	236.8	267.0	307.9
70°	155.8	158.1	159.6	161.1	163.4	165.7	173.2	183.8	199.7	220.9	252.6
72.5°	131.6	133.9	133.9	135.4	134.6	137.7	145.2	152.8	163.4	180.8	208.8
75°	107.4	107.4	108.9	109.7	110.4	113.5	116.5	122.5	130.9	144.5	161.9
77.5°	84.7	84.0	85.5	85.5	85.5	87.7	90.8	93.8	99.1	108.9	122.5
80°	62.0	62.0	63.5	64.3	62.8	63.5	65.1	68.1	71.9	78.7	86.2
82.5°	40.8	43.9	43.1	43.9	43.1	44.6	45.4	46.1	47.7	50.7	56.0
85°	25.0	25.0	25.0	25.7	25.0	25.7	25.7	25.7	26.5	28.0	30.3
87.5°	10.6	10.6	10.6	11.3	10.6	10.6	11.3	10.6	11.3	11.3	12.1
90°	16.4	15.9	16.4	15.8	15.3	14.7	14.2	13.6	14.2	12.5	10.8
92.5°	30.6	32.9	34.0	36.0	38.0	43.6	56.1	78.8	105.4	116.7	87.3
95°	72.0	77.1	87.8	98.0	108.2	138.3	204.0	272.5	336.0	299.2	206.2
97.5°	154.7	176.2	214.2	246.5	278.8	353.6	468.6	534.3	516.7	385.9	229.5
100°	376.8	418.2	475.4	515.6	555.8	622.1	668.0	648.2	536.6	362.6	213.6
102.5°	596.6	627.2	668.6	690.4	712.2	743.9	734.3	653.9	499.7	328.6	200.0
105°	741.7	763.2	789.3	796.6	804.0	793.2	736.6	618.2	455.5	302.0	194.9
107.5°	837.4	847.6	851.0	843.4	835.7	791.5	702.6	567.2	416.5	282.7	193.8
110°	885.0	880.5	864.6	844.8	825.0	753.6	649.3	519.6	384.2	272.5	196.6

TEST NUMBER: P1011812

CATALOG NUMBER: S123DIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	888.4	872.0	839.7	812.8	785.9	703.7	596.6	478.2	362.6	266.9	202.3
115°	862.4	837.4	794.9	764.0	733.2	649.9	551.3	446.5	348.5	266.3	208.5
117.5°	815.9	788.1	743.9	711.9	679.9	603.4	516.2	425.5	338.8	266.9	216.4
120°	767.7	736.0	691.3	662.6	634.0	566.0	489.5	409.7	332.6	269.1	225.5
122.5°	716.2	688.4	649.9	623.8	597.8	536.0	468.6	396.6	328.6	273.1	234.0
125°	673.1	648.2	611.9	589.2	566.6	512.2	450.4	385.9	325.2	277.1	243.1
127.5°	636.3	614.8	581.9	561.0	540.0	490.1	434.0	375.7	323.5	281.6	250.4
130°	604.6	584.2	554.1	534.8	515.6	469.7	418.7	367.7	321.8	286.1	257.8
132.5°	576.8	556.4	528.6	510.5	492.4	450.4	404.6	360.4	321.3	289.5	264.6
135°	546.2	529.2	501.4	485.2	469.1	432.3	392.1	354.1	320.7	292.9	270.3
137.5°	517.3	499.7	475.9	461.4	447.0	414.2	380.2	348.5	319.6	295.2	274.8
140°	487.8	472.0	450.4	438.2	426.1	398.9	370.0	343.4	319.0	297.5	278.2
142.5°	458.4	444.8	427.2	417.0	406.8	384.2	360.4	338.8	317.9	299.2	281.6
145°	432.3	420.4	406.3	398.0	389.8	371.7	353.0	334.9	316.7	299.7	283.9
147.5°	409.1	400.6	389.3	383.4	377.4	362.1	346.8	330.9	315.0	299.7	285.6
150°	390.4	384.2	375.7	370.3	364.9	353.0	340.0	326.9	312.8	299.7	286.1
152.5°	375.1	369.4	363.2	359.0	354.7	344.5	333.7	322.4	309.9	298.0	287.3
155°	361.5	357.0	351.9	348.5	345.1	336.6	327.5	317.9	306.5	296.9	287.3
157.5°	349.0	345.6	341.1	338.2	335.4	328.6	320.7	312.8	303.7	295.2	287.8
160°	338.3	334.9	330.9	328.9	326.9	321.3	315.0	307.7	300.3	294.1	287.8
162.5°	326.9	324.1	321.8	320.1	318.4	313.3	308.2	302.6	296.9	291.8	287.3
165°	317.3	315.0	312.8	311.4	309.9	306.0	302.6	298.0	293.5	289.5	286.1
167.5°	307.7	306.0	304.8	303.7	302.6	300.3	297.5	293.5	290.1	287.3	285.6
170°	299.2	298.0	297.5	296.9	296.3	294.1	292.4	289.5	286.7	285.0	283.9
172.5°	292.4	291.2	291.2	291.0	290.7	289.0	287.8	285.6	283.9	283.3	283.3
175°	286.1	285.6	285.6	285.6	285.6	284.4	283.9	282.7	281.6	281.6	282.2
177.5°	282.2	281.6	282.2	282.2	282.2	281.6	281.0	280.5	279.9	280.5	281.6
180°	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9

TEST NUMBER: P1011812

CATALOG NUMBER: S123DIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	801.8	799.5	799.5	798.0	793.5	785.1	784.4	785.9	781.4	776.8	770.0
5°	841.1	826.7	822.2	817.7	808.6	793.5	787.4	782.1	773.8	764.0	753.4
7.5°	874.4	854.0	847.9	839.6	821.5	800.3	786.7	775.3	764.0	750.4	737.5
10°	916.0	886.5	872.1	860.0	835.1	805.6	785.1	768.5	750.4	733.7	717.1
12.5°	962.9	915.2	910.7	881.2	852.5	808.6	783.6	759.4	735.2	714.8	697.4
15°	1002.2	950.0	931.1	911.5	856.2	801.8	777.6	750.4	722.4	700.4	674.7
17.5°	1027.2	984.1	944.0	917.5	860.0	811.6	764.7	733.7	704.2	674.0	652.8
20°	1057.5	994.7	959.9	924.3	867.6	804.1	757.2	718.6	682.3	655.0	629.3
22.5°	1087.7	1003.0	974.2	935.7	869.1	796.5	743.5	705.0	663.4	636.1	608.1
25°	1084.7	1015.1	967.4	934.9	854.0	789.7	727.7	682.3	643.7	608.9	580.9
27.5°	1087.0	1001.5	953.1	915.2	843.4	779.9	711.0	663.4	623.3	587.0	557.5
30°	1087.7	981.1	938.7	893.3	823.7	756.4	692.1	643.7	601.3	562.0	535.5
32.5°	1085.4	964.4	911.5	870.6	792.7	733.7	670.2	618.7	575.6	539.3	514.4
35°	1080.1	944.7	883.5	832.0	760.9	701.2	649.8	596.8	550.7	517.4	488.6
37.5°	1065.8	923.6	854.0	803.3	723.9	663.4	618.0	574.1	529.5	490.1	465.9
40°	1055.2	894.8	824.5	769.3	683.8	624.8	587.0	545.4	501.5	465.9	442.5
42.5°	1031.0	867.6	794.2	728.4	644.5	583.9	548.4	515.1	477.3	442.5	421.3
45°	991.6	838.1	757.2	690.6	601.3	543.9	511.3	484.1	450.8	417.5	396.4
47.5°	936.4	795.7	717.8	651.3	559.0	500.7	468.2	447.8	421.3	393.3	375.2
50°	876.7	749.6	677.7	611.9	518.1	461.4	429.6	410.7	393.3	367.6	350.2
52.5°	798.8	700.4	631.6	568.8	474.3	419.8	391.8	378.2	360.0	341.9	326.8
55°	723.1	636.9	580.2	520.4	431.1	380.5	353.2	338.9	328.3	313.2	301.0
57.5°	635.4	577.9	525.7	471.2	391.1	344.9	319.2	301.8	295.0	288.2	276.8
60°	554.4	510.6	468.2	422.8	349.5	307.9	282.9	269.3	262.5	257.9	250.4
62.5°	480.3	446.3	410.0	373.7	307.1	269.3	250.4	236.8	230.7	229.9	223.1
65°	409.2	385.0	355.5	320.0	267.8	234.5	216.3	208.0	201.2	201.2	195.9
67.5°	338.1	321.5	298.0	273.1	232.2	201.2	184.6	177.0	173.2	173.2	169.4
70°	281.4	270.0	248.9	226.9	191.4	167.9	155.1	148.3	146.0	146.7	143.7
72.5°	228.4	216.3	198.9	183.0	156.6	139.2	130.1	122.5	118.8	119.5	118.8
75°	177.0	170.9	155.8	143.7	122.5	110.4	102.1	98.3	95.3	96.1	94.6
77.5°	133.1	124.1	115.7	107.4	94.6	84.7	77.9	74.1	71.9	71.9	71.9
80°	90.8	89.3	82.4	77.9	67.3	59.8	54.5	53.7	51.4	51.4	51.4
82.5°	59.0	55.2	51.4	48.4	42.4	37.8	35.6	34.0	33.3	32.5	34.0
85°	32.5	30.3	28.7	25.7	23.4	21.2	18.9	18.2	17.4	18.2	17.4
87.5°	12.9	10.6	10.6	9.8	9.1	8.3	8.3	6.8	6.8	6.1	6.1
90°	9.1	7.4	6.8	6.2	5.1	3.4	2.3	1.1	2.3	3.4	5.1
92.5°	57.2	39.1	34.0	28.9	23.2	18.1	12.5	8.5	12.5	18.1	23.2
95°	121.8	73.7	62.6	51.6	36.8	27.2	21.0	19.3	21.0	27.2	36.8
97.5°	131.5	83.9	71.7	59.5	44.8	36.3	31.2	30.6	31.2	36.3	44.8
100°	129.8	90.1	79.0	68.0	54.4	46.5	42.5	41.9	42.5	46.5	54.4
102.5°	132.0	97.5	87.6	77.6	65.7	58.4	55.0	53.8	55.0	58.4	65.7
105°	136.6	106.0	97.2	88.4	77.6	70.8	67.4	65.7	67.4	70.8	77.6
107.5°	143.9	116.7	108.5	100.3	90.1	83.3	79.9	78.2	79.9	83.3	90.1
110°	153.5	128.1	120.2	112.2	102.6	96.3	93.5	91.8	93.5	96.3	102.6

TEST NUMBER: P1011812

CATALOG NUMBER: S123DIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	163.2	140.0	132.4	124.7	115.0	108.8	106.0	104.3	106.0	108.8	115.0
115°	173.9	152.4	144.8	137.1	127.5	121.8	118.4	116.2	118.4	121.8	127.5
117.5°	185.3	163.7	156.6	149.6	138.8	133.7	130.9	128.1	130.9	133.7	138.8
120°	196.0	175.6	168.6	161.5	150.7	145.1	142.2	140.5	142.2	145.1	150.7
122.5°	207.4	187.5	179.8	172.2	162.0	155.8	153.0	151.3	153.0	155.8	162.0
125°	218.1	198.3	190.6	183.0	172.2	166.0	162.6	161.5	162.6	166.0	172.2
127.5°	227.8	208.5	200.8	193.2	181.3	175.1	171.1	169.4	171.1	175.1	181.3
130°	236.3	217.6	210.0	202.3	190.4	183.6	178.5	176.8	178.5	183.6	190.4
132.5°	243.6	225.5	218.2	210.8	198.9	190.4	184.7	182.4	184.7	190.4	198.9
135°	251.0	233.4	225.8	218.1	206.2	197.7	191.5	189.2	191.5	197.7	206.2
137.5°	256.1	239.1	232.0	224.9	213.0	204.0	197.7	195.5	197.7	204.0	213.0
140°	261.2	244.8	237.7	230.6	219.3	210.2	204.5	201.7	204.5	210.2	219.3
142.5°	265.2	249.3	242.8	236.3	224.9	217.0	210.8	208.5	210.8	217.0	224.9
145°	268.6	253.8	247.3	240.8	231.2	222.7	217.6	215.9	217.6	222.7	231.2
147.5°	271.4	257.8	252.2	246.5	236.8	229.5	224.4	223.2	224.4	229.5	236.8
150°	274.2	261.2	256.1	251.0	243.1	235.7	231.2	230.6	231.2	235.7	243.1
152.5°	275.9	265.2	260.4	255.5	248.7	242.5	238.0	238.0	238.0	242.5	248.7
155°	278.2	268.6	264.6	260.6	254.4	248.7	245.3	245.3	245.3	248.7	254.4
157.5°	279.3	271.4	268.3	265.2	259.5	254.4	251.6	251.0	251.6	254.4	259.5
160°	281.0	274.2	271.4	268.6	264.6	260.1	257.8	257.8	257.8	260.1	264.6
162.5°	281.6	275.9	273.6	271.4	268.0	264.6	262.9	262.9	262.9	264.6	268.0
165°	282.2	277.6	275.6	273.7	271.4	268.6	267.4	268.0	267.4	268.6	271.4
167.5°	282.2	278.8	277.4	275.9	274.2	272.0	271.4	272.0	271.4	272.0	274.2
170°	281.6	278.8	278.2	277.6	276.5	274.8	274.2	275.4	274.2	274.8	276.5
172.5°	281.6	279.3	279.0	278.8	278.2	277.1	277.1	277.6	277.1	277.1	278.2
175°	281.0	279.9	279.6	279.3	279.3	278.2	278.8	279.3	278.8	278.2	279.3
177.5°	280.5	279.9	279.9	279.9	279.9	279.3	279.9	280.5	279.9	279.3	279.9
180°	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9

TEST NUMBER: P1011812

CATALOG NUMBER: S123DIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	768.5	767.7	769.3	764.7	757.2	753.4	742.8	740.5	739.8	740.5	741.3
5°	747.3	746.6	744.3	736.7	727.7	720.9	708.0	707.2	702.7	698.2	700.4
7.5°	726.9	723.9	719.3	709.5	697.4	689.8	679.2	671.7	665.6	661.9	658.8
10°	706.5	701.9	697.4	684.5	669.4	658.1	645.2	639.2	632.4	629.3	626.3
12.5°	680.0	675.5	667.1	652.0	642.9	628.6	615.7	609.7	605.9	599.8	596.0
15°	658.8	649.8	645.2	629.3	610.4	608.9	585.5	583.9	576.4	576.4	570.3
17.5°	634.6	627.8	619.5	603.6	590.0	576.4	564.3	559.7	552.9	551.4	548.4
20°	611.2	602.1	599.1	583.2	568.8	552.2	539.3	534.8	531.8	528.7	531.0
22.5°	587.0	579.4	571.8	557.5	546.9	530.2	522.7	518.1	513.6	512.1	512.8
25°	563.5	556.7	549.1	534.8	523.4	509.8	503.0	500.7	498.5	498.5	497.7
27.5°	540.8	534.0	527.2	514.4	503.0	493.2	487.9	485.6	483.3	484.9	486.4
30°	517.4	511.3	505.3	493.9	484.9	475.8	472.8	471.2	470.5	474.3	474.3
32.5°	496.2	490.9	486.4	475.8	466.7	459.1	456.9	457.6	458.4	460.6	462.2
35°	474.3	470.5	465.9	456.9	449.3	442.5	443.3	443.3	444.8	448.5	451.6
37.5°	454.6	449.3	445.5	438.0	431.9	425.9	428.1	430.4	431.9	436.4	438.0
40°	431.1	428.9	425.9	418.3	413.0	412.2	413.0	414.5	417.5	419.8	422.1
42.5°	412.2	409.2	405.4	399.4	394.8	395.6	396.4	397.9	399.4	403.2	405.4
45°	391.1	388.8	385.8	380.5	376.7	377.4	378.2	378.2	379.7	384.3	385.8
47.5°	367.6	368.4	364.6	359.3	357.0	357.0	357.0	358.5	362.3	363.8	364.6
50°	344.9	343.4	342.7	337.4	335.8	335.1	335.8	336.6	341.9	341.1	343.4
52.5°	320.7	320.7	320.0	316.9	314.7	314.7	313.2	316.9	318.4	320.0	322.2
55°	297.3	295.0	294.2	292.7	289.7	288.9	290.5	295.0	296.5	298.0	300.3
57.5°	271.5	271.5	270.0	267.8	267.8	267.8	267.8	270.8	273.1	274.6	279.1
60°	248.1	245.1	242.8	242.8	242.8	242.0	246.6	246.6	251.1	251.9	253.4
62.5°	220.1	218.6	217.1	217.8	217.1	218.6	220.1	223.1	223.9	226.2	228.4
65°	193.6	193.6	192.1	196.7	193.6	193.6	197.4	197.4	198.9	201.2	204.2
67.5°	167.9	168.7	167.2	167.2	168.7	169.4	170.2	173.2	174.0	177.0	180.8
70°	141.4	143.0	143.7	142.2	143.7	145.2	146.7	147.5	150.5	152.0	154.3
72.5°	118.0	119.5	117.2	118.0	118.8	120.3	121.0	122.5	124.1	128.6	130.1
75°	94.6	93.8	93.0	96.1	94.6	97.6	98.3	98.3	99.8	103.6	105.1
77.5°	72.6	72.6	73.4	71.9	74.1	73.4	74.1	76.4	78.7	78.7	84.7
80°	50.7	52.2	52.2	52.2	52.9	53.7	52.2	56.0	56.7	56.7	59.0
82.5°	32.5	33.3	32.5	34.0	34.0	35.6	34.8	35.6	37.1	38.6	39.3
85°	17.4	17.4	18.9	18.9	18.2	18.9	18.2	18.9	20.4	20.4	21.2
87.5°	6.1	6.1	6.1	6.1	6.8	6.1	6.8	6.8	6.1	6.1	8.3
90°	6.2	6.8	7.4	9.1	10.8	12.5	14.2	13.6	14.2	14.7	15.3
92.5°	28.9	34.0	39.1	57.2	87.3	116.7	105.4	78.8	56.1	43.6	38.0
95°	51.6	62.6	73.7	121.8	206.2	299.2	336.0	272.5	204.0	138.3	108.2
97.5°	59.5	71.7	83.9	131.5	229.5	385.9	516.7	534.3	468.6	353.6	278.8
100°	68.0	79.0	90.1	129.8	213.6	362.6	536.6	648.2	668.0	622.1	555.8
102.5°	77.6	87.6	97.5	132.0	200.0	328.6	499.7	653.9	734.3	743.9	712.2
105°	88.4	97.2	106.0	136.6	194.9	302.0	455.5	618.2	736.6	793.2	804.0
107.5°	100.3	108.5	116.7	143.9	193.8	282.7	416.5	567.2	702.6	791.5	835.7
110°	112.2	120.2	128.1	153.5	196.6	272.5	384.2	519.6	649.3	753.6	825.0

TEST NUMBER: P1011812

CATALOG NUMBER: S123DIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	124.7	132.4	140.0	163.2	202.3	266.9	362.6	478.2	596.6	703.7	785.9
115°	137.1	144.8	152.4	173.9	208.5	266.3	348.5	446.5	551.3	649.9	733.2
117.5°	149.6	156.6	163.7	185.3	216.4	266.9	338.8	425.5	516.2	603.4	679.9
120°	161.5	168.6	175.6	196.0	225.5	269.1	332.6	409.7	489.5	566.0	634.0
122.5°	172.2	179.8	187.5	207.4	234.0	273.1	328.6	396.6	468.6	536.0	597.8
125°	183.0	190.6	198.3	218.1	243.1	277.1	325.2	385.9	450.4	512.2	566.6
127.5°	193.2	200.8	208.5	227.8	250.4	281.6	323.5	375.7	434.0	490.1	540.0
130°	202.3	210.0	217.6	236.3	257.8	286.1	321.8	367.7	418.7	469.7	515.6
132.5°	210.8	218.2	225.5	243.6	264.6	289.5	321.3	360.4	404.6	450.4	492.4
135°	218.1	225.8	233.4	251.0	270.3	292.9	320.7	354.1	392.1	432.3	469.1
137.5°	224.9	232.0	239.1	256.1	274.8	295.2	319.6	348.5	380.2	414.2	447.0
140°	230.6	237.7	244.8	261.2	278.2	297.5	319.0	343.4	370.0	398.9	426.1
142.5°	236.3	242.8	249.3	265.2	281.6	299.2	317.9	338.8	360.4	384.2	406.8
145°	240.8	247.3	253.8	268.6	283.9	299.7	316.7	334.9	353.0	371.7	389.8
147.5°	246.5	252.2	257.8	271.4	285.6	299.7	315.0	330.9	346.8	362.1	377.4
150°	251.0	256.1	261.2	274.2	286.1	299.7	312.8	326.9	340.0	353.0	364.9
152.5°	255.5	260.4	265.2	275.9	287.3	298.0	309.9	322.4	333.7	344.5	354.7
155°	260.6	264.6	268.6	278.2	287.3	296.9	306.5	317.9	327.5	336.6	345.1
157.5°	265.2	268.3	271.4	279.3	287.8	295.2	303.7	312.8	320.7	328.6	335.4
160°	268.6	271.4	274.2	281.0	287.8	294.1	300.3	307.7	315.0	321.3	326.9
162.5°	271.4	273.6	275.9	281.6	287.3	291.8	296.9	302.6	308.2	313.3	318.4
165°	273.7	275.6	277.6	282.2	286.1	289.5	293.5	298.0	302.6	306.0	309.9
167.5°	275.9	277.4	278.8	282.2	285.6	287.3	290.1	293.5	297.5	300.3	302.6
170°	277.6	278.2	278.8	281.6	283.9	285.0	286.7	289.5	292.4	294.1	296.3
172.5°	278.8	279.0	279.3	281.6	283.3	283.3	283.9	285.6	287.8	289.0	290.7
175°	279.3	279.6	279.9	281.0	282.2	281.6	281.6	282.7	283.9	284.4	285.6
177.5°	279.9	279.9	279.9	280.5	281.6	280.5	279.9	280.5	281.0	281.6	282.2
180°	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9

TEST NUMBER: P1011812

CATALOG NUMBER: S123DIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	740.5	741.3	738.2	736.0	742.0	738.2	738.2	739.0	737.5	739.8	739.0
5°	698.9	699.7	694.4	695.9	692.9	692.1	691.4	695.9	695.1	694.4	695.9
7.5°	658.1	658.1	655.8	654.3	654.3	652.0	655.0	654.3	655.8	655.8	658.1
10°	624.0	625.5	621.8	618.0	617.2	618.0	618.0	618.7	619.5	624.8	624.0
12.5°	596.0	593.8	593.0	590.8	587.0	585.5	583.9	592.3	590.0	590.0	590.0
15°	565.0	570.3	569.6	562.8	561.3	564.3	562.8	562.8	570.3	569.6	568.8
17.5°	548.4	546.9	545.4	541.6	542.3	541.6	542.3	542.3	546.9	546.9	546.9
20°	529.5	526.5	526.5	524.9	524.9	522.7	525.7	526.5	529.5	529.5	530.2
22.5°	512.8	510.6	510.6	509.8	511.3	508.3	511.3	512.1	512.1	514.4	514.4
25°	498.5	497.0	497.0	498.5	498.5	498.5	498.5	501.5	499.2	500.0	499.2
27.5°	485.6	486.4	487.1	487.9	487.1	487.9	488.6	490.1	490.9	490.1	488.6
30°	473.5	475.8	476.5	476.5	478.0	478.8	479.6	479.6	480.3	478.0	479.6
32.5°	464.4	464.4	465.9	466.7	468.2	469.0	469.0	470.5	469.7	467.5	468.2
35°	451.6	451.6	454.6	456.1	458.4	457.6	458.4	458.4	459.1	457.6	455.4
37.5°	438.7	440.2	440.2	443.3	444.0	444.8	444.0	445.5	444.8	443.3	442.5
40°	423.6	422.8	423.6	425.9	426.6	426.6	426.6	428.1	428.1	428.1	427.4
42.5°	404.7	406.9	406.2	408.5	407.7	407.7	409.2	410.7	411.5	409.2	410.0
45°	386.5	386.5	388.0	388.0	388.8	388.8	391.8	390.3	391.8	390.3	391.1
47.5°	366.9	367.6	367.6	368.4	369.9	371.4	369.9	370.6	370.6	371.4	369.9
50°	344.9	344.9	346.4	348.7	351.7	350.2	349.5	352.5	350.2	350.2	348.7
52.5°	322.2	324.5	325.3	327.5	329.8	330.5	331.3	329.8	330.5	328.3	329.0
55°	300.3	301.0	304.1	306.3	308.6	308.6	307.9	308.6	309.4	306.3	306.3
57.5°	278.4	280.6	283.7	283.7	286.7	286.7	285.9	285.9	286.7	284.4	283.7
60°	254.9	257.2	261.0	261.0	265.5	266.3	264.7	263.2	263.2	261.0	261.7
62.5°	229.9	232.2	234.5	238.3	241.3	239.8	242.8	239.8	240.5	236.0	236.0
65°	208.0	208.8	212.5	216.3	216.3	217.8	216.3	217.1	214.8	214.8	211.8
67.5°	182.3	182.3	186.1	189.9	193.6	193.6	193.6	191.4	191.4	189.1	189.1
70°	159.6	158.8	162.6	164.9	167.2	167.9	166.4	165.7	164.1	161.9	161.1
72.5°	131.6	133.1	136.9	138.4	142.2	141.4	145.2	140.7	140.7	136.9	136.2
75°	106.7	108.2	111.9	114.2	116.5	116.5	118.8	116.5	113.5	111.9	111.2
77.5°	84.7	84.0	87.0	90.8	91.5	90.8	92.3	91.5	88.5	88.5	87.0
80°	60.5	62.8	65.8	65.1	68.1	67.3	67.3	65.8	65.8	63.5	65.1
82.5°	40.1	42.4	43.1	42.4	43.1	44.6	45.4	44.6	44.6	43.1	43.9
85°	21.2	21.2	22.7	23.4	22.7	22.7	23.4	25.7	24.2	22.7	24.2
87.5°	6.8	6.1	6.1	6.8	6.1	6.1	6.8	6.8	7.6	7.6	7.6
90°	15.8	16.4	15.9	16.4	17.0	16.4	17.0	16.4	15.9	16.4	15.8
92.5°	36.0	34.0	32.9	30.6	31.2	30.0	31.2	30.6	32.9	34.0	36.0
95°	98.0	87.8	77.1	72.0	68.0	65.7	68.0	72.0	77.1	87.8	98.0
97.5°	246.5	214.2	176.2	154.7	141.1	134.9	141.1	154.7	176.2	214.2	246.5
100°	515.6	475.4	418.2	376.8	354.7	355.3	354.7	376.8	418.2	475.4	515.6
102.5°	690.4	668.6	627.2	596.6	579.1	562.6	579.1	596.6	627.2	668.6	690.4
105°	796.6	789.3	763.2	741.7	723.6	720.7	723.6	741.7	763.2	789.3	796.6
107.5°	843.4	851.0	847.6	837.4	830.1	823.8	830.1	837.4	847.6	851.0	843.4
110°	844.8	864.6	880.5	885.0	883.9	882.8	883.9	885.0	880.5	864.6	844.8

TEST NUMBER: P1011812

CATALOG NUMBER: S123DIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	812.8	839.7	872.0	888.4	894.1	894.7	894.1	888.4	872.0	839.7	812.8
115°	764.0	794.9	837.4	862.4	873.7	876.5	873.7	862.4	837.4	794.9	764.0
117.5°	711.9	743.9	788.1	815.9	832.9	836.9	832.9	815.9	788.1	743.9	711.9
120°	662.6	691.3	736.0	767.7	781.3	784.7	781.3	767.7	736.0	691.3	662.6
122.5°	623.8	649.9	688.4	716.2	731.5	736.0	731.5	716.2	688.4	649.9	623.8
125°	589.2	611.9	648.2	673.1	687.3	691.3	687.3	673.1	648.2	611.9	589.2
127.5°	561.0	581.9	614.8	636.3	649.3	652.7	649.3	636.3	614.8	581.9	561.0
130°	534.8	554.1	584.2	604.6	616.5	621.0	616.5	604.6	584.2	554.1	534.8
132.5°	510.5	528.6	556.4	576.8	587.0	589.8	587.0	576.8	556.4	528.6	510.5
135°	485.2	501.4	529.2	546.2	556.4	560.4	556.4	546.2	529.2	501.4	485.2
137.5°	461.4	475.9	499.7	517.3	525.8	529.2	525.8	517.3	499.7	475.9	461.4
140°	438.2	450.4	472.0	487.8	496.9	496.3	496.9	487.8	472.0	450.4	438.2
142.5°	417.0	427.2	444.8	458.4	466.3	465.7	466.3	458.4	444.8	427.2	417.0
145°	398.0	406.3	420.4	432.3	436.9	438.0	436.9	432.3	420.4	406.3	398.0
147.5°	383.4	389.3	400.6	409.1	413.6	414.2	413.6	409.1	400.6	389.3	383.4
150°	370.3	375.7	384.2	390.4	393.8	393.8	393.8	390.4	384.2	375.7	370.3
152.5°	359.0	363.2	369.4	375.1	376.8	376.8	376.8	375.1	369.4	363.2	359.0
155°	348.5	351.9	357.0	361.5	362.6	363.2	362.6	361.5	357.0	351.9	348.5
157.5°	338.2	341.1	345.6	349.0	350.2	350.2	350.2	349.0	345.6	341.1	338.2
160°	328.9	330.9	334.9	338.3	338.3	337.7	338.3	338.3	334.9	330.9	328.9
162.5°	320.1	321.8	324.1	326.9	326.9	326.4	326.9	326.9	324.1	321.8	320.1
165°	311.4	312.8	315.0	317.3	316.7	316.7	316.7	317.3	315.0	312.8	311.4
167.5°	303.7	304.8	306.0	307.7	307.1	307.1	307.1	307.7	306.0	304.8	303.7
170°	296.9	297.5	298.0	299.2	298.6	298.6	298.6	299.2	298.0	297.5	296.9
172.5°	291.0	291.2	291.2	292.4	291.2	290.7	291.2	292.4	291.2	291.2	291.0
175°	285.6	285.6	285.6	286.1	285.6	285.0	285.6	286.1	285.6	285.6	285.6
177.5°	282.2	282.2	281.6	282.2	281.0	281.0	281.0	282.2	281.6	282.2	282.2
180°	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9

TEST NUMBER: P1011812

CATALOG NUMBER: S123DIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	741.3	742.8	743.5	740.5	738.2	742.0	747.3	751.1	754.1	757.9	760.2
5°	697.4	702.7	702.7	704.2	706.5	710.3	720.1	726.9	733.0	737.5	741.3
7.5°	660.3	664.1	666.4	670.2	674.0	679.2	690.6	700.4	709.5	714.8	720.9
10°	627.1	630.1	633.9	636.1	642.9	650.5	664.9	673.2	683.8	692.1	699.7
12.5°	595.3	605.9	608.1	607.4	613.4	621.8	636.1	649.0	660.3	668.7	677.0
15°	572.6	576.4	580.9	580.2	593.0	595.3	607.4	622.5	637.6	642.9	650.5
17.5°	547.6	553.7	558.2	560.5	564.3	572.6	583.9	595.3	615.0	615.7	635.4
20°	528.0	534.0	537.0	540.1	542.3	552.2	562.0	574.9	590.8	599.1	609.7
22.5°	515.1	518.1	520.4	522.7	525.7	531.0	543.1	557.5	568.1	577.1	583.9
25°	500.0	503.0	506.0	507.5	509.8	512.8	521.9	533.3	548.4	554.4	561.3
27.5°	489.4	489.4	490.9	490.9	493.9	497.0	503.8	514.4	526.5	534.0	543.1
30°	478.0	477.3	478.0	477.3	476.5	481.1	487.1	496.2	504.5	513.6	519.6
32.5°	466.7	465.9	465.9	466.7	463.7	465.9	469.0	477.3	486.4	490.9	497.7
35°	454.6	453.1	453.1	453.1	451.6	450.1	453.1	460.6	466.7	472.8	478.0
37.5°	442.5	440.2	440.2	438.7	437.2	434.9	434.9	441.0	449.3	451.6	458.4
40°	425.9	425.9	424.3	423.6	422.1	420.6	418.3	423.6	431.1	433.4	438.7
42.5°	409.2	406.9	406.2	406.2	406.2	403.9	402.4	406.2	410.7	414.5	417.5
45°	390.3	388.8	389.5	388.8	387.3	386.5	385.8	387.3	392.6	394.1	397.9
47.5°	369.9	369.1	369.1	368.4	367.6	368.4	365.3	369.1	370.6	372.2	375.2
50°	348.7	347.9	347.2	346.4	346.4	347.2	346.4	346.4	349.5	351.0	354.0
52.5°	327.5	325.3	325.3	324.5	324.5	323.0	324.5	325.3	326.8	328.3	329.8
55°	304.8	304.8	302.6	302.6	301.0	301.0	301.8	301.0	304.1	305.6	305.6
57.5°	282.9	279.9	280.6	279.1	277.6	276.8	276.8	278.4	279.9	279.9	281.4
60°	259.4	256.4	255.7	252.6	254.2	251.9	252.6	252.6	255.7	254.2	255.7
62.5°	236.0	232.2	229.9	228.4	228.4	229.2	227.7	226.9	228.4	229.9	233.0
65°	211.0	208.8	206.5	204.2	204.2	203.5	205.0	202.7	202.0	202.7	204.2
67.5°	185.3	183.0	180.8	178.5	179.3	177.0	175.5	177.8	176.2	177.0	178.5
70°	160.4	158.8	154.3	152.8	152.0	152.8	152.0	150.5	152.8	152.0	152.8
72.5°	135.4	133.9	131.6	127.8	127.8	127.1	126.3	126.3	125.6	125.6	125.6
75°	111.2	108.2	105.9	105.1	103.6	102.9	102.1	100.6	101.4	102.1	100.6
77.5°	86.2	82.4	81.7	81.7	79.4	79.4	80.2	79.4	78.7	78.7	78.7
80°	63.5	60.5	60.5	59.0	57.5	57.5	57.5	57.5	56.7	56.0	56.7
82.5°	40.8	40.1	39.3	39.3	40.8	37.8	39.3	38.6	37.8	37.8	37.1
85°	22.7	23.4	22.7	23.4	21.9	22.7	22.7	22.7	21.9	22.7	21.2
87.5°	8.3	8.3	8.3	9.1	9.1	9.1	9.1	9.1	9.8	9.1	9.1
90°	15.3	14.7	14.2	13.6	14.2	12.5	10.8	9.1	7.4	6.8	6.2
92.5°	38.0	43.6	56.1	78.8	105.4	116.7	87.3	57.2	39.1	34.0	28.9
95°	108.2	138.3	204.0	272.5	336.0	299.2	206.2	121.8	73.7	62.6	51.6
97.5°	278.8	353.6	468.6	534.3	516.7	385.9	229.5	131.5	83.9	71.7	59.5
100°	555.8	622.1	668.0	648.2	536.6	362.6	213.6	129.8	90.1	79.0	68.0
102.5°	712.2	743.9	734.3	653.9	499.7	328.6	200.0	132.0	97.5	87.6	77.6
105°	804.0	793.2	736.6	618.2	455.5	302.0	194.9	136.6	106.0	97.2	88.4
107.5°	835.7	791.5	702.6	567.2	416.5	282.7	193.8	143.9	116.7	108.5	100.3
110°	825.0	753.6	649.3	519.6	384.2	272.5	196.6	153.5	128.1	120.2	112.2

TEST NUMBER: P1011812

CATALOG NUMBER: S123DIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	785.9	703.7	596.6	478.2	362.6	266.9	202.3	163.2	140.0	132.4	124.7
115°	733.2	649.9	551.3	446.5	348.5	266.3	208.5	173.9	152.4	144.8	137.1
117.5°	679.9	603.4	516.2	425.5	338.8	266.9	216.4	185.3	163.7	156.6	149.6
120°	634.0	566.0	489.5	409.7	332.6	269.1	225.5	196.0	175.6	168.6	161.5
122.5°	597.8	536.0	468.6	396.6	328.6	273.1	234.0	207.4	187.5	179.8	172.2
125°	566.6	512.2	450.4	385.9	325.2	277.1	243.1	218.1	198.3	190.6	183.0
127.5°	540.0	490.1	434.0	375.7	323.5	281.6	250.4	227.8	208.5	200.8	193.2
130°	515.6	469.7	418.7	367.7	321.8	286.1	257.8	236.3	217.6	210.0	202.3
132.5°	492.4	450.4	404.6	360.4	321.3	289.5	264.6	243.6	225.5	218.2	210.8
135°	469.1	432.3	392.1	354.1	320.7	292.9	270.3	251.0	233.4	225.8	218.1
137.5°	447.0	414.2	380.2	348.5	319.6	295.2	274.8	256.1	239.1	232.0	224.9
140°	426.1	398.9	370.0	343.4	319.0	297.5	278.2	261.2	244.8	237.7	230.6
142.5°	406.8	384.2	360.4	338.8	317.9	299.2	281.6	265.2	249.3	242.8	236.3
145°	389.8	371.7	353.0	334.9	316.7	299.7	283.9	268.6	253.8	247.3	240.8
147.5°	377.4	362.1	346.8	330.9	315.0	299.7	285.6	271.4	257.8	252.2	246.5
150°	364.9	353.0	340.0	326.9	312.8	299.7	286.1	274.2	261.2	256.1	251.0
152.5°	354.7	344.5	333.7	322.4	309.9	298.0	287.3	275.9	265.2	260.4	255.5
155°	345.1	336.6	327.5	317.9	306.5	296.9	287.3	278.2	268.6	264.6	260.6
157.5°	335.4	328.6	320.7	312.8	303.7	295.2	287.8	279.3	271.4	268.3	265.2
160°	326.9	321.3	315.0	307.7	300.3	294.1	287.8	281.0	274.2	271.4	268.6
162.5°	318.4	313.3	308.2	302.6	296.9	291.8	287.3	281.6	275.9	273.6	271.4
165°	309.9	306.0	302.6	298.0	293.5	289.5	286.1	282.2	277.6	275.6	273.7
167.5°	302.6	300.3	297.5	293.5	290.1	287.3	285.6	282.2	278.8	277.4	275.9
170°	296.3	294.1	292.4	289.5	286.7	285.0	283.9	281.6	278.8	278.2	277.6
172.5°	290.7	289.0	287.8	285.6	283.9	283.3	283.3	281.6	279.3	279.0	278.8
175°	285.6	284.4	283.9	282.7	281.6	281.6	282.2	281.0	279.9	279.6	279.3
177.5°	282.2	281.6	281.0	280.5	279.9	280.5	281.6	280.5	279.9	279.9	279.9
180°	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9

TEST NUMBER: P1011812

CATALOG NUMBER: S123DIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	780.6	780.6	780.6	780.6
2.5°	764.0	766.2	773.8	782.9
5°	748.8	754.9	765.5	779.9
7.5°	732.2	741.3	756.4	774.6
10°	713.3	726.1	745.1	767.7
12.5°	692.9	709.5	733.7	757.2
15°	680.0	696.6	718.6	744.3
17.5°	655.0	674.7	697.4	733.7
20°	629.3	651.3	680.8	717.1
22.5°	609.7	633.1	661.1	699.7
25°	586.2	610.4	640.7	680.8
27.5°	561.3	585.5	619.5	661.9
30°	542.3	565.8	598.3	643.7
32.5°	519.6	542.3	576.4	624.0
35°	493.9	519.6	552.2	600.6
37.5°	474.3	497.7	531.8	577.9
40°	453.1	473.5	506.8	552.2
42.5°	430.4	453.1	481.8	527.2
45°	409.2	425.9	455.4	498.5
47.5°	386.5	405.4	428.1	461.4
50°	362.3	378.2	403.2	425.9
52.5°	338.9	351.7	372.9	390.3
55°	313.9	326.8	342.7	353.2
57.5°	290.5	299.5	310.1	316.9
60°	261.7	270.8	277.6	284.4
62.5°	236.0	242.8	246.6	250.4
65°	209.5	213.3	215.6	218.6
67.5°	180.8	184.6	185.3	189.9
70°	154.3	155.1	156.6	158.8
72.5°	129.3	130.9	130.1	131.6
75°	103.6	105.1	103.6	105.1
77.5°	78.7	80.2	80.2	82.4
80°	56.7	57.5	58.2	58.2
82.5°	37.1	39.3	37.8	38.6
85°	21.2	21.9	21.9	22.7
87.5°	9.8	10.6	9.8	11.3
90°	5.1	3.4	2.3	1.1
92.5°	23.2	18.1	12.5	8.5
95°	36.8	27.2	21.0	19.3
97.5°	44.8	36.3	31.2	30.6
100°	54.4	46.5	42.5	41.9
102.5°	65.7	58.4	55.0	53.8
105°	77.6	70.8	67.4	65.7
107.5°	90.1	83.3	79.9	78.2
110°	102.6	96.3	93.5	91.8

TEST NUMBER: P1011812

CATALOG NUMBER: S123DIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	115.0	108.8	106.0	104.3
115°	127.5	121.8	118.4	116.2
117.5°	138.8	133.7	130.9	128.1
120°	150.7	145.1	142.2	140.5
122.5°	162.0	155.8	153.0	151.3
125°	172.2	166.0	162.6	161.5
127.5°	181.3	175.1	171.1	169.4
130°	190.4	183.6	178.5	176.8
132.5°	198.9	190.4	184.7	182.4
135°	206.2	197.7	191.5	189.2
137.5°	213.0	204.0	197.7	195.5
140°	219.3	210.2	204.5	201.7
142.5°	224.9	217.0	210.8	208.5
145°	231.2	222.7	217.6	215.9
147.5°	236.8	229.5	224.4	223.2
150°	243.1	235.7	231.2	230.6
152.5°	248.7	242.5	238.0	238.0
155°	254.4	248.7	245.3	245.3
157.5°	259.5	254.4	251.6	251.0
160°	264.6	260.1	257.8	257.8
162.5°	268.0	264.6	262.9	262.9
165°	271.4	268.6	267.4	268.0
167.5°	274.2	272.0	271.4	272.0
170°	276.5	274.8	274.2	275.4
172.5°	278.2	277.1	277.1	277.6
175°	279.3	278.2	278.8	279.3
177.5°	279.9	279.3	279.9	280.5
180°	279.9	279.9	279.9	279.9

(END OF REPORT)