

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011888

Luminaire Tested: S123DIP-B560D805UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011888
REPORT IS A COMBINATION OF REPORTS P990212 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D805UB50-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5015.0 lumens
Efficiency: N/A
Efficacy: 111.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011888

CATALOG NUMBER: S123DIP-B560D805UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1011888

CATALOG NUMBER: S123DIP-B560D805UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46	46	46
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39	39	39
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	41	39	38	33	33	33
3	81	72	65	59	74	66	60	55	55	51	47	46	42	40	37	34	32	28	28	28
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24	24	24
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25	21	21	21
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22	19	19	19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19	17	17	17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17	15	15	15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	16	13	13	13
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12	12	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8149	8149	8149	8149
5°	8155	9389	8179	7008
10°	8103	11363	8110	6120
15°	7991	13475	8055	5509
20°	7895	15514	7911	5068
25°	7751	15905	7768	4839
30°	7649	13141	7649	4689
35°	7523	8788	7475	4556
40°	7370	6344	7279	4353
45°	7179	5026	6973	4100
50°	6716	4267	6477	3852
55°	6208	3750	5956	3575
60°	5691	3266	5390	3284
65°	5125	2795	4876	2897
70°	4538	2321	4235	2442
75°	3880	1750	3629	1885
80°	3067	1168	2828	1238
85°	2113	536	1691	488

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 13142 cd/sqm

TEST NUMBER: P1011888

CATALOG NUMBER: S123DIP-B560D805UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.5	1.5
10°-20°	239.1	4.8
20°-30°	402.4	8.0
30°-40°	454.7	9.1
40°-50°	407.3	8.1
50°-60°	328.8	6.6
60°-70°	229.1	4.6
70°-80°	120.2	2.4
80°-90°	30.8	0.6
90°-100°	196.8	3.9
100°-110°	576.2	11.5
110°-120°	562.6	11.2
120°-130°	448.1	8.9
130°-140°	353.5	7.0
140°-150°	263.7	5.3
150°-160°	183.9	3.7
160°-170°	108.0	2.2
170°-180°	35.1	0.7
0°-30°	716.0	14.3
0°-40°	1170.7	23.3
0°-60°	1906.8	38.0
0°-90°	2287.0	45.6
90°-120°	1335.6	26.6
90°-150°	2400.9	47.9
90°-180°	2728.0	54.4
0°-180°	5015.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	757	757	757	757	757	
5°	756	899	759	671	756	72
15°	722	1339	728	547	722	204
25°	660	1589	662	483	660	305
35°	582	856	579	444	582	365
45°	483	462	470	377	483	370
55°	343	314	329	299	343	307
65°	212	204	202	211	212	211
75°	102	105	95	113	102	109
85°	22	24	18	22	22	25
90°	2	21	2	21	2	3
95°	25	85	25	85	25	26
105°	85	934	85	934	85	90
115°	150	1136	150	1136	150	149
125°	209	896	209	896	209	186
135°	245	726	245	726	245	189
145°	280	568	280	568	280	175
155°	318	471	318	471	318	146
165°	347	410	347	410	347	98
175°	362	369	362	369	362	34
180°	363	363	363	363	363	

TEST NUMBER: P1011888

CATALOG NUMBER: S123DIP-B560D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1
2.5°	759.3	765.2	768.1	772.5	776.9	783.5	785.7	789.4	787.9	790.8	792.3
5°	756.4	766.6	775.4	786.4	796.7	804.0	811.4	823.1	831.9	833.4	840.0
7.5°	751.2	765.9	781.3	796.7	816.5	828.2	841.4	857.6	870.8	892.1	900.1
10°	744.6	765.2	787.2	808.4	835.6	853.9	870.1	897.2	924.3	946.4	966.9
12.5°	734.3	760.0	788.6	820.2	855.4	876.7	898.7	934.6	975.7	1009.4	1031.5
15°	721.9	754.1	790.8	824.6	863.5	903.1	926.5	966.9	1025.6	1057.1	1113.6
17.5°	711.6	744.6	781.3	834.1	886.9	926.5	943.4	1017.5	1057.9	1110.7	1174.5
20°	695.5	737.3	784.2	837.0	905.3	929.5	964.0	1038.8	1088.7	1157.6	1236.1
22.5°	678.6	723.3	779.8	834.8	911.1	936.8	983.8	1043.2	1122.4	1190.6	1277.2
25°	660.2	708.7	765.9	831.2	906.0	943.4	987.4	1060.8	1146.6	1232.5	1312.4
27.5°	641.9	694.7	754.1	819.4	892.1	936.1	980.1	1056.4	1166.4	1259.6	1361.6
30°	624.3	677.1	736.5	803.3	879.6	922.1	964.0	1059.3	1181.8	1286.7	1389.5
32.5°	605.2	659.5	721.9	777.6	854.7	900.1	947.1	1059.3	1191.4	1302.9	1396.8
35°	582.5	638.2	691.8	747.5	823.8	874.5	927.3	1052.0	1200.2	1308.0	1366.0
37.5°	560.5	609.6	655.8	710.1	790.1	844.4	905.3	1043.2	1195.8	1286.0	1302.2
40°	535.5	584.7	622.1	672.7	757.1	820.2	881.8	1031.5	1176.7	1233.9	1187.0
42.5°	511.3	550.2	582.5	631.6	723.3	785.0	851.7	1010.2	1139.3	1151.0	1045.4
45°	483.4	511.3	539.9	595.7	686.7	749.7	823.8	979.4	1079.1	1045.4	911.9
47.5°	447.5	472.4	504.0	555.3	647.8	713.1	783.5	939.8	991.8	921.4	775.4
50°	413.0	434.3	463.6	513.5	606.7	670.5	745.3	877.4	903.1	792.3	668.3
52.5°	378.5	394.7	423.3	473.2	566.3	628.0	696.2	813.6	798.9	680.1	570.0
55°	342.6	356.5	383.7	432.8	519.4	578.1	643.4	735.1	696.9	584.0	495.9
57.5°	307.4	322.1	349.9	391.0	472.4	529.7	581.8	653.6	596.4	506.2	428.4
60°	275.8	288.3	309.6	349.9	424.0	470.2	517.9	567.1	519.4	432.1	372.7
62.5°	242.8	254.6	274.4	311.0	374.9	416.0	454.1	494.5	441.6	377.8	325.0
65°	212.0	221.5	239.9	273.6	325.7	359.5	390.3	418.2	375.6	316.9	277.3
67.5°	184.1	192.2	207.6	237.7	281.7	305.9	330.9	354.3	318.4	271.4	237.7
70°	154.1	160.7	174.6	196.6	231.8	256.8	275.1	292.7	260.4	223.0	200.3
72.5°	127.6	134.3	143.1	165.8	190.0	205.4	225.2	234.8	216.4	185.6	162.9
75°	102.0	107.1	115.2	129.8	152.6	162.9	175.3	182.7	165.8	145.3	131.3
77.5°	80.0	82.2	88.0	98.3	113.7	125.4	135.0	139.4	127.6	114.4	102.7
80°	56.5	59.4	63.8	72.6	84.4	88.0	93.9	99.0	91.7	80.0	72.6
82.5°	37.4	41.1	43.3	47.0	54.3	58.7	60.2	64.6	58.0	53.6	50.6
85°	22.0	23.5	24.2	26.4	30.1	32.3	34.5	35.2	33.7	33.0	30.1
87.5°	11.0	11.0	11.0	12.5	13.2	14.7	15.4	15.4	15.4	14.7	13.9
90°	1.5	2.9	4.4	6.6	8.1	8.8	9.5	11.7	13.9	16.2	18.4
92.5°	11.0	16.2	23.5	30.1	37.4	44.0	50.7	74.1	113.1	151.2	136.5
95°	25.0	27.2	35.2	47.7	66.8	81.1	95.4	157.8	267.2	387.6	435.3
97.5°	39.6	40.4	47.0	58.0	77.1	92.9	108.7	170.3	297.3	499.9	669.5
100°	54.3	55.1	60.2	70.5	88.1	102.4	116.7	168.1	276.8	469.8	695.2
102.5°	69.7	71.2	75.6	85.2	100.6	113.4	126.3	171.1	259.2	425.8	647.5
105°	85.2	87.4	91.8	100.6	114.5	125.9	137.3	176.9	252.5	391.3	590.2
107.5°	101.3	103.5	107.9	116.7	129.9	140.6	151.2	186.5	251.1	366.3	539.6
110°	118.9	121.1	124.8	132.9	145.4	155.6	165.9	199.0	254.7	353.1	497.7



TEST NUMBER: P1011888

CATALOG NUMBER: S123DIP-B560D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	135.1	137.3	141.0	149.0	161.5	171.4	181.3	211.4	262.1	345.8	469.8
115°	150.5	153.4	157.8	165.2	177.7	187.6	197.5	225.4	270.2	345.0	451.5
117.5°	165.9	169.6	173.3	179.9	193.8	203.0	212.2	240.1	280.4	345.8	439.0
120°	182.1	184.3	187.9	195.3	209.2	218.4	227.6	254.0	292.2	348.7	430.9
122.5°	196.0	198.2	201.9	210.0	223.2	233.1	243.0	268.7	303.2	353.9	425.8
125°	209.2	210.7	215.1	223.2	237.1	247.0	256.9	282.6	314.9	359.0	421.4
127.5°	219.5	221.7	226.8	234.9	250.3	260.2	270.2	295.1	324.5	364.9	419.2
130°	229.1	231.3	237.9	246.7	262.1	272.0	281.9	306.1	334.0	370.7	417.0
132.5°	236.4	239.3	246.7	257.7	273.1	282.6	292.2	315.7	342.8	375.1	416.3
135°	245.2	248.1	256.2	267.2	282.6	292.6	302.5	325.2	350.2	379.5	415.5
137.5°	253.3	256.2	264.3	276.0	291.5	300.6	309.8	331.8	356.1	382.5	414.1
140°	261.4	265.0	272.4	284.1	298.8	308.0	317.1	338.4	360.5	385.4	413.3
142.5°	270.2	273.1	281.2	291.5	306.1	314.6	323.0	343.6	364.9	387.6	411.9
145°	279.7	281.9	288.5	299.5	312.0	320.4	328.9	348.0	367.8	388.4	410.4
147.5°	289.2	290.7	297.3	306.9	319.3	326.6	334.0	351.7	370.0	388.4	408.2
150°	298.8	299.5	305.4	314.9	325.2	331.8	338.4	355.3	370.7	388.4	405.2
152.5°	308.3	308.3	314.2	322.3	331.1	337.4	343.6	357.5	372.2	386.2	401.6
155°	317.9	317.9	322.3	329.6	337.7	342.8	348.0	360.5	372.2	384.7	397.2
157.5°	325.2	326.0	329.6	336.2	343.6	347.6	351.7	361.9	372.9	382.5	393.5
160°	334.0	334.0	337.0	342.8	348.0	351.6	355.3	364.1	372.9	381.0	389.1
162.5°	340.6	340.6	342.8	347.2	351.7	354.6	357.5	364.9	372.2	378.1	384.7
165°	347.2	346.5	348.0	351.7	354.6	357.2	359.7	365.6	370.7	375.1	380.3
167.5°	352.4	351.7	352.4	355.3	357.5	359.4	361.2	365.6	370.0	372.2	375.9
170°	356.8	355.3	356.1	358.3	359.7	360.4	361.2	364.9	367.8	369.3	371.5
172.5°	359.7	359.0	359.0	360.5	361.2	361.5	361.9	364.9	367.1	367.1	367.8
175°	361.9	361.2	360.5	361.9	361.9	362.3	362.7	364.1	365.6	364.9	364.9
177.5°	363.4	362.7	361.9	362.7	362.7	362.7	362.7	363.4	364.9	363.4	362.7
180°	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7

TEST NUMBER: P1011888

CATALOG NUMBER: S123DIP-B560D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1
2.5°	797.4	798.9	804.0	807.7	815.0	814.3	814.3	813.6	811.4	815.0	817.2
5°	853.2	865.7	867.1	883.3	884.0	890.6	895.0	891.3	900.1	899.4	892.8
7.5°	922.1	939.0	947.1	962.5	980.1	975.7	992.6	995.5	994.0	1001.4	1006.5
10°	997.7	1027.1	1047.6	1076.2	1083.5	1087.9	1098.9	1108.5	1127.6	1112.9	1122.4
12.5°	1084.3	1105.5	1132.7	1178.2	1200.9	1215.6	1220.7	1227.3	1240.5	1232.5	1233.2
15°	1156.9	1185.5	1231.7	1288.2	1294.8	1313.2	1308.8	1348.4	1367.4	1338.8	1355.0
17.5°	1232.5	1270.6	1325.6	1374.8	1402.7	1415.1	1426.9	1465.0	1463.5	1459.1	1462.8
20°	1280.9	1343.2	1411.5	1476.8	1484.8	1494.4	1525.9	1542.0	1539.1	1551.6	1559.7
22.5°	1349.1	1415.1	1487.8	1531.0	1549.4	1560.4	1585.3	1595.6	1600.0	1602.9	1597.8
25°	1406.3	1476.8	1530.3	1568.5	1579.5	1585.3	1593.4	1596.3	1594.1	1589.0	1593.4
27.5°	1445.2	1501.7	1538.4	1556.0	1550.1	1540.6	1525.2	1514.9	1492.2	1481.2	1494.4
30°	1461.3	1486.3	1497.3	1467.9	1438.6	1415.1	1385.8	1331.5	1288.9	1301.4	1284.5
32.5°	1435.7	1419.5	1366.7	1291.2	1268.4	1230.3	1147.4	1083.5	1085.7	1052.0	1065.9
35°	1360.1	1286.7	1187.0	1072.5	1042.5	1021.9	930.9	917.0	887.7	856.1	864.9
37.5°	1226.6	1119.5	998.4	914.1	869.3	824.6	773.2	742.4	724.8	711.6	721.9
40°	1063.7	933.1	833.4	757.8	719.7	691.1	655.8	625.0	605.2	603.0	606.7
42.5°	903.8	793.8	702.1	630.2	617.7	584.0	561.2	537.0	531.1	521.6	526.7
45°	765.2	675.7	600.1	541.4	526.7	517.9	490.1	474.6	468.0	462.2	471.0
47.5°	664.6	570.7	515.7	480.5	465.8	451.2	435.8	425.5	420.4	421.1	420.4
50°	567.8	498.9	450.4	423.3	414.5	404.2	391.7	385.1	382.9	376.3	381.5
52.5°	488.6	438.7	405.0	379.3	372.7	365.3	355.1	351.4	346.3	344.8	344.8
55°	424.8	385.9	358.7	341.9	333.8	327.9	322.1	317.7	314.0	314.0	314.0
57.5°	374.9	341.1	321.3	306.6	303.7	297.8	291.2	291.2	286.1	285.4	287.6
60°	332.3	302.2	286.8	274.4	270.0	268.5	261.9	261.9	260.4	256.8	259.7
62.5°	289.0	267.0	253.8	244.3	239.9	239.9	234.8	231.1	231.1	231.8	230.4
65°	249.4	233.3	221.5	214.2	212.0	209.1	208.3	205.4	203.2	203.9	203.2
67.5°	214.2	201.7	193.7	187.8	184.1	182.7	180.5	180.5	179.0	179.7	176.1
70°	182.7	170.2	163.6	157.7	156.3	156.3	153.3	154.1	152.6	154.8	153.3
72.5°	150.4	140.9	135.7	133.5	132.0	131.3	129.8	128.4	127.6	129.1	128.4
75°	121.8	113.7	110.0	108.6	107.1	107.1	106.4	105.6	104.9	104.9	104.9
77.5°	94.6	89.5	85.1	86.6	84.4	85.1	82.9	82.9	83.6	82.9	82.9
80°	69.7	66.0	66.0	64.6	61.6	63.1	63.1	60.9	60.2	61.6	59.4
82.5°	46.2	45.5	44.0	43.3	41.8	42.5	41.8	41.1	40.3	41.8	40.3
85°	27.1	27.1	26.4	24.9	26.4	25.7	24.9	24.9	24.2	24.2	24.2
87.5°	13.9	12.5	12.5	11.7	12.5	11.0	11.7	11.0	10.3	11.0	10.3
90°	17.6	18.4	19.1	19.8	20.6	21.3	20.6	21.3	22.0	21.3	22.0
92.5°	102.0	72.7	56.5	49.2	46.6	44.0	42.6	39.6	40.4	38.9	40.4
95°	353.1	264.3	179.1	140.2	127.0	113.8	99.8	93.2	88.1	85.2	88.1
97.5°	692.3	607.1	458.1	361.2	319.4	277.5	228.3	200.4	182.8	174.7	182.8
100°	839.9	865.5	806.1	720.2	668.0	615.9	541.8	488.2	459.6	460.3	459.6
102.5°	847.2	951.4	963.9	922.8	894.6	866.3	812.7	773.0	750.3	729.0	750.3
105°	800.9	954.4	1027.8	1041.7	1032.2	1022.7	988.9	961.0	937.5	933.8	937.5
107.5°	734.9	910.3	1025.6	1082.9	1092.8	1102.7	1098.3	1085.1	1075.5	1067.4	1075.5
110°	673.2	841.3	976.4	1068.9	1094.6	1120.3	1140.8	1146.7	1145.3	1143.8	1145.3

TEST NUMBER: P1011888

CATALOG NUMBER: S123DIP-B560D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	619.6	773.0	911.8	1018.2	1053.1	1088.0	1129.8	1151.1	1158.5	1159.2	1158.5
115°	578.5	714.3	842.1	950.0	990.0	1030.0	1085.1	1117.4	1132.0	1135.7	1132.0
117.5°	551.3	668.8	781.9	881.0	922.4	963.9	1021.2	1057.2	1079.2	1084.3	1079.2
120°	530.8	634.3	733.4	821.5	858.6	895.6	953.6	994.8	1012.4	1016.8	1012.4
122.5°	513.9	607.1	694.5	774.5	808.3	842.1	892.0	927.9	947.8	953.6	947.8
125°	499.9	583.6	663.7	734.1	763.5	792.9	839.9	872.2	890.5	895.6	890.5
127.5°	486.7	562.3	635.0	699.6	726.8	754.0	796.5	824.4	841.3	845.7	841.3
130°	476.5	542.5	608.6	668.1	693.0	718.0	756.9	783.3	798.7	804.6	798.7
132.5°	466.9	524.2	583.6	638.0	661.4	684.9	720.9	747.4	760.6	764.2	760.6
135°	458.8	508.0	560.1	607.9	628.8	649.7	685.7	707.7	720.9	726.1	720.9
137.5°	451.5	492.6	536.7	579.2	598.0	616.7	647.5	670.3	681.3	685.7	681.3
140°	444.9	479.4	516.8	552.1	567.8	583.6	611.5	632.1	643.8	643.1	643.8
142.5°	439.0	466.9	497.7	527.1	540.3	553.5	576.3	593.9	604.2	603.5	604.2
145°	433.9	457.4	481.6	505.1	515.8	526.4	544.7	560.1	566.0	567.5	566.0
147.5°	428.7	449.3	469.1	488.9	496.6	504.4	519.0	530.0	535.9	536.7	535.9
150°	423.6	440.5	457.4	472.8	479.8	486.7	497.7	505.8	510.2	510.2	510.2
152.5°	417.7	432.4	446.4	459.6	465.1	470.6	478.7	486.0	488.2	488.2	488.2
155°	411.9	424.3	436.1	447.1	451.5	455.9	462.5	468.4	469.8	470.6	469.8
157.5°	405.2	415.5	425.8	434.6	438.3	442.0	447.8	452.2	453.7	453.7	453.7
160°	398.6	408.2	416.3	423.6	426.2	428.7	433.9	438.3	438.3	437.5	438.3
162.5°	392.0	399.4	406.0	412.6	414.8	417.0	419.9	423.6	423.6	422.9	423.6
165°	386.2	392.0	396.4	401.6	403.4	405.2	408.2	411.1	410.4	410.4	410.4
167.5°	380.3	385.4	389.1	392.0	393.5	395.0	396.4	398.6	397.9	397.9	397.9
170°	375.1	378.8	381.0	384.0	384.7	385.4	386.2	387.6	386.9	386.9	386.9
172.5°	370.0	372.9	374.4	376.6	377.0	377.3	377.3	378.8	377.3	376.6	377.3
175°	366.3	367.8	368.5	370.0	370.0	370.0	370.0	370.7	370.0	369.3	370.0
177.5°	363.4	364.1	364.9	365.6	365.6	365.6	364.9	365.6	364.1	364.1	364.1
180°	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7

TEST NUMBER: P1011888

CATALOG NUMBER: S123DIP-B560D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1
2.5°	811.4	813.6	807.7	806.2	806.2	809.2	807.0	787.2	790.8	786.4	785.0
5°	900.9	896.5	890.6	887.7	884.0	873.7	873.0	850.3	845.9	831.2	824.6
7.5°	999.2	995.5	977.9	975.7	974.2	964.7	940.5	916.3	898.7	881.8	865.7
10°	1111.4	1100.4	1092.3	1076.2	1068.1	1054.9	1023.4	1000.6	970.6	944.9	911.1
12.5°	1246.4	1233.9	1206.8	1195.0	1184.8	1148.1	1116.6	1090.9	1032.2	1014.6	972.8
15°	1345.4	1319.0	1316.1	1290.4	1288.9	1248.6	1188.4	1160.6	1115.1	1050.5	1007.2
17.5°	1452.5	1429.1	1410.7	1379.9	1375.5	1337.4	1293.4	1225.1	1175.2	1113.6	1058.6
20°	1531.0	1518.6	1487.0	1474.6	1448.9	1416.6	1371.1	1286.7	1225.9	1164.2	1096.7
22.5°	1593.4	1580.9	1556.0	1539.1	1524.4	1482.6	1428.3	1356.4	1272.8	1192.1	1122.4
25°	1592.7	1589.0	1578.7	1570.7	1559.7	1528.8	1483.4	1414.4	1321.2	1232.5	1135.6
27.5°	1502.4	1512.7	1530.3	1539.1	1536.9	1532.5	1506.8	1448.9	1365.2	1259.6	1151.0
30°	1314.6	1352.0	1385.1	1429.1	1442.3	1474.6	1489.2	1456.2	1389.5	1291.2	1170.8
32.5°	1090.1	1144.4	1216.3	1240.5	1282.3	1344.7	1414.4	1426.9	1385.1	1309.5	1183.3
35°	894.3	939.0	994.8	1032.9	1070.3	1171.6	1259.6	1335.9	1349.8	1300.0	1180.4
37.5°	740.2	771.8	820.9	853.2	887.7	974.2	1097.5	1196.5	1266.2	1267.7	1172.3
40°	628.7	642.6	685.2	708.7	741.7	816.5	926.5	1055.7	1157.6	1204.6	1151.0
42.5°	532.6	550.9	586.2	603.8	625.0	690.3	763.0	885.5	1011.6	1112.1	1111.4
45°	475.4	488.6	504.7	519.4	543.6	582.5	665.4	757.1	878.1	991.8	1036.6
47.5°	424.8	437.2	453.4	457.8	473.9	510.6	561.2	641.2	754.1	867.1	951.5
50°	382.2	392.5	403.5	411.6	418.9	449.0	487.1	554.6	644.8	754.1	859.1
52.5°	349.2	356.5	366.1	370.5	377.1	399.1	428.4	478.3	552.4	652.2	754.1
55°	318.4	323.5	329.4	336.7	339.7	355.8	378.5	421.1	476.1	565.6	662.4
57.5°	289.8	292.0	295.6	300.0	303.7	317.7	337.5	366.1	414.5	483.4	575.1
60°	257.5	263.4	265.6	270.0	272.2	283.2	298.6	322.8	360.2	419.6	488.6
62.5°	230.4	234.0	237.7	239.9	245.0	248.7	261.2	283.2	314.0	358.0	420.4
65°	206.1	207.6	209.8	212.0	213.5	217.9	229.6	244.3	267.8	306.6	355.1
67.5°	178.3	179.7	182.7	183.4	184.9	190.7	197.3	209.8	229.6	259.0	298.6
70°	151.1	153.3	154.8	156.3	158.5	160.7	168.0	178.3	193.7	214.2	245.0
72.5°	127.6	129.8	129.8	131.3	130.6	133.5	140.9	148.2	158.5	175.3	202.5
75°	104.2	104.2	105.6	106.4	107.1	110.0	113.0	118.8	126.9	140.1	157.0
77.5°	82.2	81.4	82.9	82.9	82.9	85.1	88.0	91.0	96.1	105.6	118.8
80°	60.2	60.2	61.6	62.4	60.9	61.6	63.1	66.0	69.7	76.3	83.6
82.5°	39.6	42.5	41.8	42.5	41.8	43.3	44.0	44.8	46.2	49.2	54.3
85°	24.2	24.2	24.2	24.9	24.2	24.9	24.9	24.9	25.7	27.1	29.3
87.5°	10.3	10.3	10.3	11.0	10.3	10.3	11.0	10.3	11.0	11.0	11.7
90°	21.3	20.6	21.3	20.6	19.8	19.1	18.4	17.6	18.4	16.2	13.9
92.5°	39.6	42.6	44.0	46.6	49.2	56.5	72.7	102.0	136.5	151.2	113.1
95°	93.2	99.8	113.8	127.0	140.2	179.1	264.3	353.1	435.3	387.6	267.2
97.5°	200.4	228.3	277.5	319.4	361.2	458.1	607.1	692.3	669.5	499.9	297.3
100°	488.2	541.8	615.9	668.0	720.2	806.1	865.5	839.9	695.2	469.8	276.8
102.5°	773.0	812.7	866.3	894.6	922.8	963.9	951.4	847.2	647.5	425.8	259.2
105°	961.0	988.9	1022.7	1032.2	1041.7	1027.8	954.4	800.9	590.2	391.3	252.5
107.5°	1085.1	1098.3	1102.7	1092.8	1082.9	1025.6	910.3	734.9	539.6	366.3	251.1
110°	1146.7	1140.8	1120.3	1094.6	1068.9	976.4	841.3	673.2	497.7	353.1	254.7

TEST NUMBER: P1011888

CATALOG NUMBER: S123DIP-B560D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1151.1	1129.8	1088.0	1053.1	1018.2	911.8	773.0	619.6	469.8	345.8	262.1
115°	1117.4	1085.1	1030.0	990.0	950.0	842.1	714.3	578.5	451.5	345.0	270.2
117.5°	1057.2	1021.2	963.9	922.4	881.0	781.9	668.8	551.3	439.0	345.8	280.4
120°	994.8	953.6	895.6	858.6	821.5	733.4	634.3	530.8	430.9	348.7	292.2
122.5°	927.9	892.0	842.1	808.3	774.5	694.5	607.1	513.9	425.8	353.9	303.2
125°	872.2	839.9	792.9	763.5	734.1	663.7	583.6	499.9	421.4	359.0	314.9
127.5°	824.4	796.5	754.0	726.8	699.6	635.0	562.3	486.7	419.2	364.9	324.5
130°	783.3	756.9	718.0	693.0	668.1	608.6	542.5	476.5	417.0	370.7	334.0
132.5°	747.4	720.9	684.9	661.4	638.0	583.6	524.2	466.9	416.3	375.1	342.8
135°	707.7	685.7	649.7	628.8	607.9	560.1	508.0	458.8	415.5	379.5	350.2
137.5°	670.3	647.5	616.7	598.0	579.2	536.7	492.6	451.5	414.1	382.5	356.1
140°	632.1	611.5	583.6	567.8	552.1	516.8	479.4	444.9	413.3	385.4	360.5
142.5°	593.9	576.3	553.5	540.3	527.1	497.7	466.9	439.0	411.9	387.6	364.9
145°	560.1	544.7	526.4	515.8	505.1	481.6	457.4	433.9	410.4	388.4	367.8
147.5°	530.0	519.0	504.4	496.6	488.9	469.1	449.3	428.7	408.2	388.4	370.0
150°	505.8	497.7	486.7	479.8	472.8	457.4	440.5	423.6	405.2	388.4	370.7
152.5°	486.0	478.7	470.6	465.1	459.6	446.4	432.4	417.7	401.6	386.2	372.2
155°	468.4	462.5	455.9	451.5	447.1	436.1	424.3	411.9	397.2	384.7	372.2
157.5°	452.2	447.8	442.0	438.3	434.6	425.8	415.5	405.2	393.5	382.5	372.9
160°	438.3	433.9	428.7	426.2	423.6	416.3	408.2	398.6	389.1	381.0	372.9
162.5°	423.6	419.9	417.0	414.8	412.6	406.0	399.4	392.0	384.7	378.1	372.2
165°	411.1	408.2	405.2	403.4	401.6	396.4	392.0	386.2	380.3	375.1	370.7
167.5°	398.6	396.4	395.0	393.5	392.0	389.1	385.4	380.3	375.9	372.2	370.0
170°	387.6	386.2	385.4	384.7	384.0	381.0	378.8	375.1	371.5	369.3	367.8
172.5°	378.8	377.3	377.3	377.0	376.6	374.4	372.9	370.0	367.8	367.1	367.1
175°	370.7	370.0	370.0	370.0	370.0	368.5	367.8	366.3	364.9	364.9	365.6
177.5°	365.6	364.9	365.6	365.6	365.6	364.9	364.1	363.4	362.7	363.4	364.9
180°	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7

TEST NUMBER: P1011888

CATALOG NUMBER: S123DIP-B560D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1
2.5°	777.6	775.4	775.4	774.0	769.6	761.5	760.8	762.2	757.8	753.4	746.8
5°	815.8	801.8	797.4	793.0	784.2	769.6	763.7	758.6	750.5	740.9	730.7
7.5°	848.1	828.2	822.4	814.3	796.7	776.2	763.0	751.9	740.9	727.7	715.3
10°	888.4	859.8	845.9	834.1	809.9	781.3	761.5	745.3	727.7	711.6	695.5
12.5°	933.9	887.7	883.3	854.7	826.8	784.2	760.0	736.5	713.1	693.3	676.4
15°	972.0	921.4	903.1	884.0	830.4	777.6	754.1	727.7	700.6	679.3	654.4
17.5°	996.2	954.4	915.5	889.9	834.1	787.2	741.7	711.6	683.0	653.6	633.1
20°	1025.6	964.7	930.9	896.5	841.4	779.8	734.3	696.9	661.7	635.3	610.4
22.5°	1054.9	972.8	944.9	907.5	842.9	772.5	721.1	683.7	643.4	617.0	589.8
25°	1052.0	984.5	938.3	906.7	828.2	765.9	705.7	661.7	624.3	590.6	563.4
27.5°	1054.2	971.3	924.3	887.7	818.0	756.4	689.6	643.4	604.5	569.3	540.7
30°	1054.9	951.5	910.4	866.4	798.9	733.6	671.3	624.3	583.2	545.1	519.4
32.5°	1052.7	935.4	884.0	844.4	768.8	711.6	650.0	600.1	558.3	523.1	498.9
35°	1047.6	916.3	856.9	807.0	738.0	680.1	630.2	578.8	534.1	501.8	473.9
37.5°	1033.7	895.7	828.2	779.1	702.1	643.4	599.4	556.8	513.5	475.4	451.9
40°	1023.4	867.9	799.6	746.1	663.2	606.0	569.3	528.9	486.4	451.9	429.2
42.5°	999.9	841.4	770.3	706.5	625.0	566.3	531.9	499.6	462.9	429.2	408.6
45°	961.8	812.8	734.3	669.8	583.2	527.5	495.9	469.5	437.2	405.0	384.4
47.5°	908.2	771.8	696.2	631.6	542.1	485.6	454.1	434.3	408.6	381.5	363.9
50°	850.3	727.0	657.3	593.5	502.5	447.5	416.7	398.3	381.5	356.5	339.7
52.5°	774.7	679.3	612.6	551.7	460.0	407.2	380.0	366.8	349.2	331.6	316.9
55°	701.3	617.7	562.7	504.7	418.2	369.0	342.6	328.7	318.4	303.7	292.0
57.5°	616.2	560.5	509.9	457.0	379.3	334.5	309.6	292.7	286.1	279.5	268.5
60°	537.7	495.2	454.1	410.1	338.9	298.6	274.4	261.2	254.6	250.2	242.8
62.5°	465.8	432.8	397.6	362.4	297.8	261.2	242.8	229.6	223.8	223.0	216.4
65°	396.9	373.4	344.8	310.3	259.7	227.4	209.8	201.7	195.1	195.1	190.0
67.5°	327.9	311.8	289.0	264.8	225.2	195.1	179.0	171.7	168.0	168.0	164.3
70°	272.9	261.9	241.4	220.1	185.6	162.9	150.4	143.8	141.6	142.3	139.4
72.5°	221.5	209.8	192.9	177.5	151.9	135.0	126.2	118.8	115.2	115.9	115.2
75°	171.7	165.8	151.1	139.4	118.8	107.1	99.0	95.4	92.4	93.2	91.7
77.5°	129.1	120.3	112.2	104.2	91.7	82.2	75.6	71.9	69.7	69.7	69.7
80°	88.0	86.6	80.0	75.6	65.3	58.0	52.8	52.1	49.9	49.9	49.9
82.5°	57.2	53.6	49.9	47.0	41.1	36.7	34.5	33.0	32.3	31.5	33.0
85°	31.5	29.3	27.9	24.9	22.7	20.5	18.3	17.6	16.9	17.6	16.9
87.5°	12.5	10.3	10.3	9.5	8.8	8.1	8.1	6.6	6.6	5.9	5.9
90°	11.7	9.5	8.8	8.1	6.6	4.4	2.9	1.5	2.9	4.4	6.6
92.5°	74.1	50.7	44.0	37.4	30.1	23.5	16.2	11.0	16.2	23.5	30.1
95°	157.8	95.4	81.1	66.8	47.7	35.2	27.2	25.0	27.2	35.2	47.7
97.5°	170.3	108.7	92.9	77.1	58.0	47.0	40.4	39.6	40.4	47.0	58.0
100°	168.1	116.7	102.4	88.1	70.5	60.2	55.1	54.3	55.1	60.2	70.5
102.5°	171.1	126.3	113.4	100.6	85.2	75.6	71.2	69.7	71.2	75.6	85.2
105°	176.9	137.3	125.9	114.5	100.6	91.8	87.4	85.2	87.4	91.8	100.6
107.5°	186.5	151.2	140.6	129.9	116.7	107.9	103.5	101.3	103.5	107.9	116.7
110°	199.0	165.9	155.6	145.4	132.9	124.8	121.1	118.9	121.1	124.8	132.9

TEST NUMBER: P1011888

CATALOG NUMBER: S123DIP-B560D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	211.4	181.3	171.4	161.5	149.0	141.0	137.3	135.1	137.3	141.0	149.0
115°	225.4	197.5	187.6	177.7	165.2	157.8	153.4	150.5	153.4	157.8	165.2
117.5°	240.1	212.2	203.0	193.8	179.9	173.3	169.6	165.9	169.6	173.3	179.9
120°	254.0	227.6	218.4	209.2	195.3	187.9	184.3	182.1	184.3	187.9	195.3
122.5°	268.7	243.0	233.1	223.2	210.0	201.9	198.2	196.0	198.2	201.9	210.0
125°	282.6	256.9	247.0	237.1	223.2	215.1	210.7	209.2	210.7	215.1	223.2
127.5°	295.1	270.2	260.2	250.3	234.9	226.8	221.7	219.5	221.7	226.8	234.9
130°	306.1	281.9	272.0	262.1	246.7	237.9	231.3	229.1	231.3	237.9	246.7
132.5°	315.7	292.2	282.6	273.1	257.7	246.7	239.3	236.4	239.3	246.7	257.7
135°	325.2	302.5	292.6	282.6	267.2	256.2	248.1	245.2	248.1	256.2	267.2
137.5°	331.8	309.8	300.6	291.5	276.0	264.3	256.2	253.3	256.2	264.3	276.0
140°	338.4	317.1	308.0	298.8	284.1	272.4	265.0	261.4	265.0	272.4	284.1
142.5°	343.6	323.0	314.6	306.1	291.5	281.2	273.1	270.2	273.1	281.2	291.5
145°	348.0	328.9	320.4	312.0	299.5	288.5	281.9	279.7	281.9	288.5	299.5
147.5°	351.7	334.0	326.6	319.3	306.9	297.3	290.7	289.2	290.7	297.3	306.9
150°	355.3	338.4	331.8	325.2	314.9	305.4	299.5	298.8	299.5	305.4	314.9
152.5°	357.5	343.6	337.4	331.1	322.3	314.2	308.3	308.3	308.3	314.2	322.3
155°	360.5	348.0	342.8	337.7	329.6	322.3	317.9	317.9	317.9	322.3	329.6
157.5°	361.9	351.7	347.6	343.6	336.2	329.6	326.0	325.2	326.0	329.6	336.2
160°	364.1	355.3	351.6	348.0	342.8	337.0	334.0	334.0	334.0	337.0	342.8
162.5°	364.9	357.5	354.6	351.7	347.2	342.8	340.6	340.6	340.6	342.8	347.2
165°	365.6	359.7	357.2	354.6	351.7	348.0	346.5	347.2	346.5	348.0	351.7
167.5°	365.6	361.2	359.4	357.5	355.3	352.4	351.7	352.4	351.7	352.4	355.3
170°	364.9	361.2	360.4	359.7	358.3	356.1	355.3	356.8	355.3	356.1	358.3
172.5°	364.9	361.9	361.5	361.2	360.5	359.0	359.0	359.7	359.0	359.0	360.5
175°	364.1	362.7	362.3	361.9	361.9	360.5	361.2	361.9	361.2	360.5	361.9
177.5°	363.4	362.7	362.7	362.7	362.7	361.9	362.7	363.4	362.7	361.9	362.7
180°	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7

TEST NUMBER: P1011888

CATALOG NUMBER: S123DIP-B560D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1
2.5°	745.3	744.6	746.1	741.7	734.3	730.7	720.4	718.2	717.5	718.2	718.9
5°	724.8	724.1	721.9	714.5	705.7	699.1	686.7	685.9	681.5	677.1	679.3
7.5°	705.0	702.1	697.7	688.1	676.4	669.1	658.8	651.4	645.6	641.9	639.0
10°	685.2	680.8	676.4	663.9	649.2	638.2	625.8	619.9	613.3	610.4	607.4
12.5°	659.5	655.1	647.0	632.4	623.6	609.6	597.2	591.3	587.6	581.8	578.1
15°	639.0	630.2	625.8	610.4	592.0	590.6	567.8	566.3	559.0	559.0	553.1
17.5°	615.5	608.9	600.8	585.4	572.2	559.0	547.3	542.9	536.3	534.8	531.9
20°	592.8	584.0	581.0	565.6	551.7	535.5	523.1	518.7	515.7	512.8	515.0
22.5°	569.3	561.9	554.6	540.7	530.4	514.3	506.9	502.5	498.1	496.7	497.4
25°	546.5	539.9	532.6	518.7	507.7	494.5	487.8	485.6	483.4	483.4	482.7
27.5°	524.5	517.9	511.3	498.9	487.8	478.3	473.2	471.0	468.8	470.2	471.7
30°	501.8	495.9	490.1	479.0	470.2	461.4	458.5	457.0	456.3	460.0	460.0
32.5°	481.2	476.1	471.7	461.4	452.6	445.3	443.1	443.8	444.6	446.8	448.2
35°	460.0	456.3	451.9	443.1	435.8	429.2	429.9	429.9	431.4	435.0	438.0
37.5°	440.9	435.8	432.1	424.8	418.9	413.0	415.2	417.4	418.9	423.3	424.8
40°	418.2	416.0	413.0	405.7	400.6	399.8	400.6	402.0	405.0	407.2	409.4
42.5°	399.8	396.9	393.2	387.3	382.9	383.7	384.4	385.9	387.3	391.0	393.2
45°	379.3	377.1	374.1	369.0	365.3	366.1	366.8	366.8	368.3	372.7	374.1
47.5°	356.5	357.3	353.6	348.5	346.3	346.3	346.3	347.7	351.4	352.9	353.6
50°	334.5	333.1	332.3	327.2	325.7	325.0	325.7	326.5	331.6	330.9	333.1
52.5°	311.0	311.0	310.3	307.4	305.2	305.2	303.7	307.4	308.8	310.3	312.5
55°	288.3	286.1	285.4	283.9	281.0	280.2	281.7	286.1	287.6	289.0	291.2
57.5°	263.4	263.4	261.9	259.7	259.7	259.7	259.7	262.6	264.8	266.3	270.7
60°	240.6	237.7	235.5	235.5	235.5	234.8	239.2	239.2	243.6	244.3	245.8
62.5°	213.5	212.0	210.5	211.3	210.5	212.0	213.5	216.4	217.1	219.3	221.5
65°	187.8	187.8	186.3	190.7	187.8	187.8	191.5	191.5	192.9	195.1	198.1
67.5°	162.9	163.6	162.1	162.1	163.6	164.3	165.1	168.0	168.7	171.7	175.3
70°	137.2	138.7	139.4	137.9	139.4	140.9	142.3	143.1	146.0	147.5	149.7
72.5°	114.4	115.9	113.7	114.4	115.2	116.6	117.4	118.8	120.3	124.7	126.2
75°	91.7	91.0	90.2	93.2	91.7	94.6	95.4	95.4	96.8	100.5	102.0
77.5°	70.4	70.4	71.2	69.7	71.9	71.2	71.9	74.1	76.3	76.3	82.2
80°	49.2	50.6	50.6	50.6	51.4	52.1	50.6	54.3	55.0	55.0	57.2
82.5°	31.5	32.3	31.5	33.0	33.0	34.5	33.7	34.5	35.9	37.4	38.1
85°	16.9	16.9	18.3	18.3	17.6	18.3	17.6	18.3	19.8	19.8	20.5
87.5°	5.9	5.9	5.9	5.9	6.6	5.9	6.6	6.6	5.9	5.9	8.1
90°	8.1	8.8	9.5	11.7	13.9	16.2	18.4	17.6	18.4	19.1	19.8
92.5°	37.4	44.0	50.7	74.1	113.1	151.2	136.5	102.0	72.7	56.5	49.2
95°	66.8	81.1	95.4	157.8	267.2	387.6	435.3	353.1	264.3	179.1	140.2
97.5°	77.1	92.9	108.7	170.3	297.3	499.9	669.5	692.3	607.1	458.1	361.2
100°	88.1	102.4	116.7	168.1	276.8	469.8	695.2	839.9	865.5	806.1	720.2
102.5°	100.6	113.4	126.3	171.1	259.2	425.8	647.5	847.2	951.4	963.9	922.8
105°	114.5	125.9	137.3	176.9	252.5	391.3	590.2	800.9	954.4	1027.8	1041.7
107.5°	129.9	140.6	151.2	186.5	251.1	366.3	539.6	734.9	910.3	1025.6	1082.9
110°	145.4	155.6	165.9	199.0	254.7	353.1	497.7	673.2	841.3	976.4	1068.9

TEST NUMBER: P1011888

CATALOG NUMBER: S123DIP-B560D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	161.5	171.4	181.3	211.4	262.1	345.8	469.8	619.6	773.0	911.8	1018.2
115°	177.7	187.6	197.5	225.4	270.2	345.0	451.5	578.5	714.3	842.1	950.0
117.5°	193.8	203.0	212.2	240.1	280.4	345.8	439.0	551.3	668.8	781.9	881.0
120°	209.2	218.4	227.6	254.0	292.2	348.7	430.9	530.8	634.3	733.4	821.5
122.5°	223.2	233.1	243.0	268.7	303.2	353.9	425.8	513.9	607.1	694.5	774.5
125°	237.1	247.0	256.9	282.6	314.9	359.0	421.4	499.9	583.6	663.7	734.1
127.5°	250.3	260.2	270.2	295.1	324.5	364.9	419.2	486.7	562.3	635.0	699.6
130°	262.1	272.0	281.9	306.1	334.0	370.7	417.0	476.5	542.5	608.6	668.1
132.5°	273.1	282.6	292.2	315.7	342.8	375.1	416.3	466.9	524.2	583.6	638.0
135°	282.6	292.6	302.5	325.2	350.2	379.5	415.5	458.8	508.0	560.1	607.9
137.5°	291.5	300.6	309.8	331.8	356.1	382.5	414.1	451.5	492.6	536.7	579.2
140°	298.8	308.0	317.1	338.4	360.5	385.4	413.3	444.9	479.4	516.8	552.1
142.5°	306.1	314.6	323.0	343.6	364.9	387.6	411.9	439.0	466.9	497.7	527.1
145°	312.0	320.4	328.9	348.0	367.8	388.4	410.4	433.9	457.4	481.6	505.1
147.5°	319.3	326.6	334.0	351.7	370.0	388.4	408.2	428.7	449.3	469.1	488.9
150°	325.2	331.8	338.4	355.3	370.7	388.4	405.2	423.6	440.5	457.4	472.8
152.5°	331.1	337.4	343.6	357.5	372.2	386.2	401.6	417.7	432.4	446.4	459.6
155°	337.7	342.8	348.0	360.5	372.2	384.7	397.2	411.9	424.3	436.1	447.1
157.5°	343.6	347.6	351.7	361.9	372.9	382.5	393.5	405.2	415.5	425.8	434.6
160°	348.0	351.6	355.3	364.1	372.9	381.0	389.1	398.6	408.2	416.3	423.6
162.5°	351.7	354.6	357.5	364.9	372.2	378.1	384.7	392.0	399.4	406.0	412.6
165°	354.6	357.2	359.7	365.6	370.7	375.1	380.3	386.2	392.0	396.4	401.6
167.5°	357.5	359.4	361.2	365.6	370.0	372.2	375.9	380.3	385.4	389.1	392.0
170°	359.7	360.4	361.2	364.9	367.8	369.3	371.5	375.1	378.8	381.0	384.0
172.5°	361.2	361.5	361.9	364.9	367.1	367.1	367.8	370.0	372.9	374.4	376.6
175°	361.9	362.3	362.7	364.1	365.6	364.9	364.9	366.3	367.8	368.5	370.0
177.5°	362.7	362.7	362.7	363.4	364.9	363.4	362.7	363.4	364.1	364.9	365.6
180°	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7

TEST NUMBER: P1011888

CATALOG NUMBER: S123DIP-B560D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1
2.5°	718.2	718.9	716.0	713.8	719.7	716.0	716.0	716.7	715.3	717.5	716.7
5°	677.9	678.6	673.5	674.9	672.0	671.3	670.5	674.9	674.2	673.5	674.9
7.5°	638.2	638.2	636.0	634.6	634.6	632.4	635.3	634.6	636.0	636.0	638.2
10°	605.2	606.7	603.0	599.4	598.6	599.4	599.4	600.1	600.8	606.0	605.2
12.5°	578.1	575.9	575.1	572.9	569.3	567.8	566.3	574.4	572.2	572.2	572.2
15°	548.0	553.1	552.4	545.8	544.3	547.3	545.8	545.8	553.1	552.4	551.7
17.5°	531.9	530.4	528.9	525.3	526.0	525.3	526.0	526.0	530.4	530.4	530.4
20°	513.5	510.6	510.6	509.1	509.1	506.9	509.9	510.6	513.5	513.5	514.3
22.5°	497.4	495.2	495.2	494.5	495.9	493.0	495.9	496.7	496.7	498.9	498.9
25°	483.4	482.0	482.0	483.4	483.4	483.4	483.4	486.4	484.2	484.9	484.2
27.5°	471.0	471.7	472.4	473.2	472.4	473.2	473.9	475.4	476.1	475.4	473.9
30°	459.2	461.4	462.2	462.2	463.6	464.4	465.1	465.1	465.8	463.6	465.1
32.5°	450.4	450.4	451.9	452.6	454.1	454.8	454.8	456.3	455.6	453.4	454.1
35°	438.0	438.0	440.9	442.4	444.6	443.8	444.6	444.6	445.3	443.8	441.6
37.5°	425.5	427.0	427.0	429.9	430.6	431.4	430.6	432.1	431.4	429.9	429.2
40°	410.8	410.1	410.8	413.0	413.8	413.8	413.8	415.2	415.2	415.2	414.5
42.5°	392.5	394.7	393.9	396.1	395.4	395.4	396.9	398.3	399.1	396.9	397.6
45°	374.9	374.9	376.3	376.3	377.1	377.1	380.0	378.5	380.0	378.5	379.3
47.5°	355.8	356.5	356.5	357.3	358.7	360.2	358.7	359.5	359.5	360.2	358.7
50°	334.5	334.5	336.0	338.2	341.1	339.7	338.9	341.9	339.7	339.7	338.2
52.5°	312.5	314.7	315.5	317.7	319.9	320.6	321.3	319.9	320.6	318.4	319.1
55°	291.2	292.0	294.9	297.1	299.3	299.3	298.6	299.3	300.0	297.1	297.1
57.5°	270.0	272.2	275.1	275.1	278.0	278.0	277.3	277.3	278.0	275.8	275.1
60°	247.2	249.4	253.1	253.1	257.5	258.2	256.8	255.3	255.3	253.1	253.8
62.5°	223.0	225.2	227.4	231.1	234.0	232.6	235.5	232.6	233.3	228.9	228.9
65°	201.7	202.5	206.1	209.8	209.8	211.3	209.8	210.5	208.3	208.3	205.4
67.5°	176.8	176.8	180.5	184.1	187.8	187.8	187.8	185.6	185.6	183.4	183.4
70°	154.8	154.1	157.7	159.9	162.1	162.9	161.4	160.7	159.2	157.0	156.3
72.5°	127.6	129.1	132.8	134.3	137.9	137.2	140.9	136.5	136.5	132.8	132.0
75°	103.4	104.9	108.6	110.8	113.0	113.0	115.2	113.0	110.0	108.6	107.8
77.5°	82.2	81.4	84.4	88.0	88.8	88.0	89.5	88.8	85.8	85.8	84.4
80°	58.7	60.9	63.8	63.1	66.0	65.3	65.3	63.8	63.8	61.6	63.1
82.5°	38.9	41.1	41.8	41.1	41.8	43.3	44.0	43.3	43.3	41.8	42.5
85°	20.5	20.5	22.0	22.7	22.0	22.0	22.7	24.9	23.5	22.0	23.5
87.5°	6.6	5.9	5.9	6.6	5.9	5.9	6.6	6.6	7.3	7.3	7.3
90°	20.6	21.3	20.6	21.3	22.0	21.3	22.0	21.3	20.6	21.3	20.6
92.5°	46.6	44.0	42.6	39.6	40.4	38.9	40.4	39.6	42.6	44.0	46.6
95°	127.0	113.8	99.8	93.2	88.1	85.2	88.1	93.2	99.8	113.8	127.0
97.5°	319.4	277.5	228.3	200.4	182.8	174.7	182.8	200.4	228.3	277.5	319.4
100°	668.0	615.9	541.8	488.2	459.6	460.3	459.6	488.2	541.8	615.9	668.0
102.5°	894.6	866.3	812.7	773.0	750.3	729.0	750.3	773.0	812.7	866.3	894.6
105°	1032.2	1022.7	988.9	961.0	937.5	933.8	937.5	961.0	988.9	1022.7	1032.2
107.5°	1092.8	1102.7	1098.3	1085.1	1075.5	1067.4	1075.5	1085.1	1098.3	1102.7	1092.8
110°	1094.6	1120.3	1140.8	1146.7	1145.3	1143.8	1145.3	1146.7	1140.8	1120.3	1094.6

TEST NUMBER: P1011888

CATALOG NUMBER: S123DIP-B560D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1053.1	1088.0	1129.8	1151.1	1158.5	1159.2	1158.5	1151.1	1129.8	1088.0	1053.1
115°	990.0	1030.0	1085.1	1117.4	1132.0	1135.7	1132.0	1117.4	1085.1	1030.0	990.0
117.5°	922.4	963.9	1021.2	1057.2	1079.2	1084.3	1079.2	1057.2	1021.2	963.9	922.4
120°	858.6	895.6	953.6	994.8	1012.4	1016.8	1012.4	994.8	953.6	895.6	858.6
122.5°	808.3	842.1	892.0	927.9	947.8	953.6	947.8	927.9	892.0	842.1	808.3
125°	763.5	792.9	839.9	872.2	890.5	895.6	890.5	872.2	839.9	792.9	763.5
127.5°	726.8	754.0	796.5	824.4	841.3	845.7	841.3	824.4	796.5	754.0	726.8
130°	693.0	718.0	756.9	783.3	798.7	804.6	798.7	783.3	756.9	718.0	693.0
132.5°	661.4	684.9	720.9	747.4	760.6	764.2	760.6	747.4	720.9	684.9	661.4
135°	628.8	649.7	685.7	707.7	720.9	726.1	720.9	707.7	685.7	649.7	628.8
137.5°	598.0	616.7	647.5	670.3	681.3	685.7	681.3	670.3	647.5	616.7	598.0
140°	567.8	583.6	611.5	632.1	643.8	643.1	643.8	632.1	611.5	583.6	567.8
142.5°	540.3	553.5	576.3	593.9	604.2	603.5	604.2	593.9	576.3	553.5	540.3
145°	515.8	526.4	544.7	560.1	566.0	567.5	566.0	560.1	544.7	526.4	515.8
147.5°	496.6	504.4	519.0	530.0	535.9	536.7	535.9	530.0	519.0	504.4	496.6
150°	479.8	486.7	497.7	505.8	510.2	510.2	510.2	505.8	497.7	486.7	479.8
152.5°	465.1	470.6	478.7	486.0	488.2	488.2	488.2	486.0	478.7	470.6	465.1
155°	451.5	455.9	462.5	468.4	469.8	470.6	469.8	468.4	462.5	455.9	451.5
157.5°	438.3	442.0	447.8	452.2	453.7	453.7	453.7	452.2	447.8	442.0	438.3
160°	426.2	428.7	433.9	438.3	438.3	437.5	438.3	438.3	433.9	428.7	426.2
162.5°	414.8	417.0	419.9	423.6	423.6	422.9	423.6	423.6	419.9	417.0	414.8
165°	403.4	405.2	408.2	411.1	410.4	410.4	410.4	411.1	408.2	405.2	403.4
167.5°	393.5	395.0	396.4	398.6	397.9	397.9	397.9	398.6	396.4	395.0	393.5
170°	384.7	385.4	386.2	387.6	386.9	386.9	386.9	387.6	386.2	385.4	384.7
172.5°	377.0	377.3	377.3	378.8	377.3	376.6	377.3	378.8	377.3	377.3	377.0
175°	370.0	370.0	370.0	370.7	370.0	369.3	370.0	370.7	370.0	370.0	370.0
177.5°	365.6	365.6	364.9	365.6	364.1	364.1	364.1	365.6	364.9	365.6	365.6
180°	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7

TEST NUMBER: P1011888

CATALOG NUMBER: S123DIP-B560D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1
2.5°	718.9	720.4	721.1	718.2	716.0	719.7	724.8	728.5	731.4	735.1	737.3
5°	676.4	681.5	681.5	683.0	685.2	688.9	698.4	705.0	710.9	715.3	718.9
7.5°	640.4	644.1	646.3	650.0	653.6	658.8	669.8	679.3	688.1	693.3	699.1
10°	608.2	611.1	614.8	617.0	623.6	630.9	644.8	652.9	663.2	671.3	678.6
12.5°	577.3	587.6	589.8	589.1	595.0	603.0	617.0	629.4	640.4	648.5	656.6
15°	555.3	559.0	563.4	562.7	575.1	577.3	589.1	603.8	618.4	623.6	630.9
17.5°	531.1	537.0	541.4	543.6	547.3	555.3	566.3	577.3	596.4	597.2	616.2
20°	512.1	517.9	520.9	523.8	526.0	535.5	545.1	557.5	572.9	581.0	591.3
22.5°	499.6	502.5	504.7	506.9	509.9	515.0	526.7	540.7	550.9	559.7	566.3
25°	484.9	487.8	490.8	492.3	494.5	497.4	506.2	517.2	531.9	537.7	544.3
27.5°	474.6	474.6	476.1	476.1	479.0	482.0	488.6	498.9	510.6	517.9	526.7
30°	463.6	462.9	463.6	462.9	462.2	466.6	472.4	481.2	489.3	498.1	504.0
32.5°	452.6	451.9	451.9	452.6	449.7	451.9	454.8	462.9	471.7	476.1	482.7
35°	440.9	439.4	439.4	439.4	438.0	436.5	439.4	446.8	452.6	458.5	463.6
37.5°	429.2	427.0	427.0	425.5	424.0	421.8	421.8	427.7	435.8	438.0	444.6
40°	413.0	413.0	411.6	410.8	409.4	407.9	405.7	410.8	418.2	420.4	425.5
42.5°	396.9	394.7	393.9	393.9	393.9	391.7	390.3	393.9	398.3	402.0	405.0
45°	378.5	377.1	377.8	377.1	375.6	374.9	374.1	375.6	380.7	382.2	385.9
47.5°	358.7	358.0	358.0	357.3	356.5	357.3	354.3	358.0	359.5	360.9	363.9
50°	338.2	337.5	336.7	336.0	336.0	336.7	336.0	336.0	338.9	340.4	343.3
52.5°	317.7	315.5	315.5	314.7	314.7	313.3	314.7	315.5	316.9	318.4	319.9
55°	295.6	295.6	293.4	293.4	292.0	292.0	292.7	292.0	294.9	296.4	296.4
57.5°	274.4	271.4	272.2	270.7	269.2	268.5	268.5	270.0	271.4	271.4	272.9
60°	251.6	248.7	248.0	245.0	246.5	244.3	245.0	245.0	248.0	246.5	248.0
62.5°	228.9	225.2	223.0	221.5	221.5	222.3	220.8	220.1	221.5	223.0	226.0
65°	204.7	202.5	200.3	198.1	198.1	197.3	198.8	196.6	195.9	196.6	198.1
67.5°	179.7	177.5	175.3	173.1	173.9	171.7	170.2	172.4	170.9	171.7	173.1
70°	155.5	154.1	149.7	148.2	147.5	148.2	147.5	146.0	148.2	147.5	148.2
72.5°	131.3	129.8	127.6	124.0	124.0	123.2	122.5	122.5	121.8	121.8	121.8
75°	107.8	104.9	102.7	102.0	100.5	99.8	99.0	97.6	98.3	99.0	97.6
77.5°	83.6	80.0	79.2	79.2	77.0	77.0	77.8	77.0	76.3	76.3	76.3
80°	61.6	58.7	58.7	57.2	55.8	55.8	55.8	55.8	55.0	54.3	55.0
82.5°	39.6	38.9	38.1	38.1	39.6	36.7	38.1	37.4	36.7	36.7	35.9
85°	22.0	22.7	22.0	22.7	21.3	22.0	22.0	22.0	21.3	22.0	20.5
87.5°	8.1	8.1	8.1	8.8	8.8	8.8	8.8	8.8	9.5	8.8	8.8
90°	19.8	19.1	18.4	17.6	18.4	16.2	13.9	11.7	9.5	8.8	8.1
92.5°	49.2	56.5	72.7	102.0	136.5	151.2	113.1	74.1	50.7	44.0	37.4
95°	140.2	179.1	264.3	353.1	435.3	387.6	267.2	157.8	95.4	81.1	66.8
97.5°	361.2	458.1	607.1	692.3	669.5	499.9	297.3	170.3	108.7	92.9	77.1
100°	720.2	806.1	865.5	839.9	695.2	469.8	276.8	168.1	116.7	102.4	88.1
102.5°	922.8	963.9	951.4	847.2	647.5	425.8	259.2	171.1	126.3	113.4	100.6
105°	1041.7	1027.8	954.4	800.9	590.2	391.3	252.5	176.9	137.3	125.9	114.5
107.5°	1082.9	1025.6	910.3	734.9	539.6	366.3	251.1	186.5	151.2	140.6	129.9
110°	1068.9	976.4	841.3	673.2	497.7	353.1	254.7	199.0	165.9	155.6	145.4

TEST NUMBER: P1011888

CATALOG NUMBER: S123DIP-B560D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1018.2	911.8	773.0	619.6	469.8	345.8	262.1	211.4	181.3	171.4	161.5
115°	950.0	842.1	714.3	578.5	451.5	345.0	270.2	225.4	197.5	187.6	177.7
117.5°	881.0	781.9	668.8	551.3	439.0	345.8	280.4	240.1	212.2	203.0	193.8
120°	821.5	733.4	634.3	530.8	430.9	348.7	292.2	254.0	227.6	218.4	209.2
122.5°	774.5	694.5	607.1	513.9	425.8	353.9	303.2	268.7	243.0	233.1	223.2
125°	734.1	663.7	583.6	499.9	421.4	359.0	314.9	282.6	256.9	247.0	237.1
127.5°	699.6	635.0	562.3	486.7	419.2	364.9	324.5	295.1	270.2	260.2	250.3
130°	668.1	608.6	542.5	476.5	417.0	370.7	334.0	306.1	281.9	272.0	262.1
132.5°	638.0	583.6	524.2	466.9	416.3	375.1	342.8	315.7	292.2	282.6	273.1
135°	607.9	560.1	508.0	458.8	415.5	379.5	350.2	325.2	302.5	292.6	282.6
137.5°	579.2	536.7	492.6	451.5	414.1	382.5	356.1	331.8	309.8	300.6	291.5
140°	552.1	516.8	479.4	444.9	413.3	385.4	360.5	338.4	317.1	308.0	298.8
142.5°	527.1	497.7	466.9	439.0	411.9	387.6	364.9	343.6	323.0	314.6	306.1
145°	505.1	481.6	457.4	433.9	410.4	388.4	367.8	348.0	328.9	320.4	312.0
147.5°	488.9	469.1	449.3	428.7	408.2	388.4	370.0	351.7	334.0	326.6	319.3
150°	472.8	457.4	440.5	423.6	405.2	388.4	370.7	355.3	338.4	331.8	325.2
152.5°	459.6	446.4	432.4	417.7	401.6	386.2	372.2	357.5	343.6	337.4	331.1
155°	447.1	436.1	424.3	411.9	397.2	384.7	372.2	360.5	348.0	342.8	337.7
157.5°	434.6	425.8	415.5	405.2	393.5	382.5	372.9	361.9	351.7	347.6	343.6
160°	423.6	416.3	408.2	398.6	389.1	381.0	372.9	364.1	355.3	351.6	348.0
162.5°	412.6	406.0	399.4	392.0	384.7	378.1	372.2	364.9	357.5	354.6	351.7
165°	401.6	396.4	392.0	386.2	380.3	375.1	370.7	365.6	359.7	357.2	354.6
167.5°	392.0	389.1	385.4	380.3	375.9	372.2	370.0	365.6	361.2	359.4	357.5
170°	384.0	381.0	378.8	375.1	371.5	369.3	367.8	364.9	361.2	360.4	359.7
172.5°	376.6	374.4	372.9	370.0	367.8	367.1	367.1	364.9	361.9	361.5	361.2
175°	370.0	368.5	367.8	366.3	364.9	364.9	365.6	364.1	362.7	362.3	361.9
177.5°	365.6	364.9	364.1	363.4	362.7	363.4	364.9	363.4	362.7	362.7	362.7
180°	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7

TEST NUMBER: P1011888

CATALOG NUMBER: S123DIP-B560D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	757.1	757.1	757.1	757.1
2.5°	740.9	743.1	750.5	759.3
5°	726.3	732.1	742.4	756.4
7.5°	710.1	718.9	733.6	751.2
10°	691.8	704.3	722.6	744.6
12.5°	672.0	688.1	711.6	734.3
15°	659.5	675.7	696.9	721.9
17.5°	635.3	654.4	676.4	711.6
20°	610.4	631.6	660.2	695.5
22.5°	591.3	614.0	641.2	678.6
25°	568.5	592.0	621.4	660.2
27.5°	544.3	567.8	600.8	641.9
30°	526.0	548.7	580.3	624.3
32.5°	504.0	526.0	559.0	605.2
35°	479.0	504.0	535.5	582.5
37.5°	460.0	482.7	515.7	560.5
40°	439.4	459.2	491.5	535.5
42.5°	417.4	439.4	467.3	511.3
45°	396.9	413.0	441.6	483.4
47.5°	374.9	393.2	415.2	447.5
50°	351.4	366.8	391.0	413.0
52.5°	328.7	341.1	361.7	378.5
55°	304.4	316.9	332.3	342.6
57.5°	281.7	290.5	300.8	307.4
60°	253.8	262.6	269.2	275.8
62.5°	228.9	235.5	239.2	242.8
65°	203.2	206.9	209.1	212.0
67.5°	175.3	179.0	179.7	184.1
70°	149.7	150.4	151.9	154.1
72.5°	125.4	126.9	126.2	127.6
75°	100.5	102.0	100.5	102.0
77.5°	76.3	77.8	77.8	80.0
80°	55.0	55.8	56.5	56.5
82.5°	35.9	38.1	36.7	37.4
85°	20.5	21.3	21.3	22.0
87.5°	9.5	10.3	9.5	11.0
90°	6.6	4.4	2.9	1.5
92.5°	30.1	23.5	16.2	11.0
95°	47.7	35.2	27.2	25.0
97.5°	58.0	47.0	40.4	39.6
100°	70.5	60.2	55.1	54.3
102.5°	85.2	75.6	71.2	69.7
105°	100.6	91.8	87.4	85.2
107.5°	116.7	107.9	103.5	101.3
110°	132.9	124.8	121.1	118.9

TEST NUMBER: P1011888

CATALOG NUMBER: S123DIP-B560D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	149.0	141.0	137.3	135.1
115°	165.2	157.8	153.4	150.5
117.5°	179.9	173.3	169.6	165.9
120°	195.3	187.9	184.3	182.1
122.5°	210.0	201.9	198.2	196.0
125°	223.2	215.1	210.7	209.2
127.5°	234.9	226.8	221.7	219.5
130°	246.7	237.9	231.3	229.1
132.5°	257.7	246.7	239.3	236.4
135°	267.2	256.2	248.1	245.2
137.5°	276.0	264.3	256.2	253.3
140°	284.1	272.4	265.0	261.4
142.5°	291.5	281.2	273.1	270.2
145°	299.5	288.5	281.9	279.7
147.5°	306.9	297.3	290.7	289.2
150°	314.9	305.4	299.5	298.8
152.5°	322.3	314.2	308.3	308.3
155°	329.6	322.3	317.9	317.9
157.5°	336.2	329.6	326.0	325.2
160°	342.8	337.0	334.0	334.0
162.5°	347.2	342.8	340.6	340.6
165°	351.7	348.0	346.5	347.2
167.5°	355.3	352.4	351.7	352.4
170°	358.3	356.1	355.3	356.8
172.5°	360.5	359.0	359.0	359.7
175°	361.9	360.5	361.2	361.9
177.5°	362.7	361.9	362.7	363.4
180°	362.7	362.7	362.7	362.7

(END OF REPORT)